

Product phase-out WinCC V7.5 (SP1 / SP2)

MLFB	Product
6AV6381-2BC07-5AH0	WinCC RT 128, V7.5 SP2 DL
6AV6381-2BC07-5AV0	WinCC RT 128, V7.5 SP2 Asia
6AV6381-2BC07-5AX0	WinCC RT 128, V7.5 SP2
6AV6381-2BD07-5AH0	WinCC RT 512, V7.5 SP2 DL
6AV6381-2BD07-5AV0	WinCC RT 512, V7.5 SP2 Asia
6AV6381-2BD07-5AX0	WinCC RT 512, V7.5 SP2
6AV6381-2BE07-5AH0	WinCC RT 2048, V7.5 SP2 DL
6AV6381-2BE07-5AV0	WinCC RT 2048, V7.5 SP2 Asia
6AV6381-2BE07-5AX0	WinCC RT 2048, V7.5 SP2
6AV6381-2BF07-5AH0	WinCC RT 65536, V7.5 SP2 DL
6AV6381-2BF07-5AV0	WinCC RT 65536, V7.5 SP2 Asia
6AV6381-2BF07-5AX0	WinCC RT 65536, V7.5 SP2
6AV6381-2BH07-5AH0	WinCC RT 8192, V7.5 SP2 DL
6AV6381-2BH07-5AV0	WinCC RT 8192, V7.5 SP2 Asia
6AV6381-2BH07-5AX0	WinCC RT 8192, V7.5 SP2
6AV6381-2BJ07-5AH0	WinCC RT 102400, V7.5 SP2 DL
6AV6381-2BJ07-5AV0	WinCC RT 102400, V7.5 SP2 Asia
6AV6381-2BJ07-5AX0	WinCC RT 102400, V7.5 SP2
6AV6381-2BK07-5AH0	WinCC RT 153600, V7.5 SP2 DL
6AV6381-2BK07-5AV0	WinCC RT 153600, V7.5 SP2 Asia
6AV6381-2BK07-5AX0	WinCC RT 153600, V7.5 SP2
6AV6381-2BL07-5AH0	WinCC RT 262144, V7.5 SP2 DL
6AV6381-2BL07-5AV0	WinCC RT 262144, V7.5 SP2 Asia
6AV6381-2BL07-5AX0	WinCC RT 262144, V7.5 SP2
6AV6381-2BM07-5AH0	WinCC RC 128, V7.5 SP2 DL
6AV6381-2BM07-5AV0	WinCC RC 128, V7.5 SP2 Asia
6AV6381-2BM07-5AX0	WinCC RC 128, V7.5 SP2
6AV6381-2BN07-5AH0	WinCC RC 512, V7.5 SP2 DL
6AV6381-2BN07-5AV0	WinCC RC 512, V7.5 SP2 Asia
6AV6381-2BN07-5AX0	WinCC RC 512, V7.5 SP2
6AV6381-2BP07-5AH0	WinCC RC 2048, V7.5 SP2 DL
6AV6381-2BP07-5AV0	WinCC RC 2048, V7.5 SP2 Asia
6AV6381-2BP07-5AX0	WinCC RC 2048, V7.5 SP2
6AV6381-2BQ07-5AH0	WinCC RC 65536, V7.5 SP2 DL
6AV6381-2BQ07-5AV0	WinCC RC 65536, V7.5 SP2 Asia
6AV6381-2BQ07-5AX0	WinCC RC 65536, V7.5 SP2
6AV6381-2BS07-5AH0	WinCC RC 8192, V7.5 SP2 DL

6AV6381-2BS07-5AV0	WinCC RC 8192, V7.5 SP2 Asia
6AV6381-2BS07-5AX0	WinCC RC 8192, V7.5 SP2
6AV6381-2BT07-5AH0	WinCC RC 102400, V7.5 SP2 DL
6AV6381-2BT07-5AV0	WinCC RC 102400, V7.5 SP2 Asia
6AV6381-2BT07-5AX0	WinCC RC 102400, V7.5 SP2
6AV6381-2BU07-5AH0	WinCC RC 153600, V7.5 SP2 DL
6AV6381-2BU07-5AV0	WinCC RC 153600, V7.5 SP2 Asia
6AV6381-2BU07-5AX0	WinCC RC 153600, V7.5 SP2
6AV6381-2BV07-5AH0	WinCC RC 262144, V7.5 SP2 DL
6AV6381-2BV07-5AV0	WinCC RC 262144, V7.5 SP2 Asia
6AV6381-2BV07-5AX0	WinCC RC 262144, V7.5 SP2
6AV6381-2CA07-5AH0	WinCC RT Client V7.5 SP2 DL
6AV6381-2DC07-5AH0	WinCC RT 500000, V7.5 SP2 DL
6AV6381-2DC07-5AX0	WinCC RT 500000, V7.5 SP2
6AV6381-2DM07-5AH0	WinCC RC 500000, V7.5 SP2 DL
6AV6381-2DM07-5AX0	WinCC RC 500000, V7.5 SP2
6AV6381-2CB07-5AX0	WinCC RC Client V7.5 SP2
6AV6381-2CB07-5AV0	WinCC RC Client V7.5 SP2 Asia
6AV6381-2CB07-5AH0	WinCC RC Client V7.5 SP2 DL
6AV6381-2CA07-5AX0	WinCC RT Client V7.5 SP2
6AV6381-2CA07-5AV0	WinCC RT Client V7.5 SP2 Asia

6AV6371-2BD07-5AJ0	WinCC/Powerp RT 128/512 V7.5 SP2 DL
6AV6371-2BD07-5AX0	WinCC/Powerp RT 128/512 V7.5 SP2
6AV6371-2BD17-5AJ0	WinCC/Powerp RC 128/512 V7.5 SP2 DL
6AV6371-2BD17-5AX0	WinCC/Powerp RC 128/512 V7.5 SP2
6AV6371-2BG07-5AJ0	WinCC/Powerp RT 512/2048 V7.5 SP2 DL
6AV6371-2BG07-5AX0	WinCC/Powerp RT 512/2048 V7.5 SP2
6AV6371-2BG17-5AJ0	WinCC/Powerp RC 512/2048 V7.5 SP2 DL
6AV6371-2BG17-5AX0	WinCC/Powerp RC 512/2048 V7.5 SP2
6AV6371-2BM07-5AJ0	WinCC/Powerp RT 2048/8192 V7.5 SP2 DL
6AV6371-2BM07-5AX0	WinCC/Powerp RT 2048/8192 V7.5 SP2
6AV6371-2BM17-5AJ0	WinCC/Powerp RC 2048/8192 V7.5 SP2 DL
6AV6371-2BM17-5AX0	WinCC/Powerp RC 2048/8192 V7.5 SP2
6AV6371-2BN07-5AJ0	WinCC/Powerp. RT 8192/65536 V7.5SP2 DL
6AV6371-2BN07-5AX0	WinCC/Powerp RT 8192/65536 V7.5 SP2
6AV6371-2BN17-5AJ0	WinCC/Powerp RC 8192/65536 V7.5 SP2 DL
6AV6371-2BN17-5AX0	WinCC/Powerp RC 8192/65536 V7.5 SP2
6AV6371-2BP07-5AJ0	WinCC/Powerp RT 65536/102400 V7.5SP2 DL

6AV6371-2BP07-5AX0	WinCC/Powerp RT 65536/102400 V7.5 SP2
6AV6371-2BP17-5AJ0	WinCC/Powerp RC 65536/102400 V7.5 SP2 DL
6AV6371-2BP17-5AX0	WinCC/Powerp RC 65536/102400 V7.5 SP2
6AV6371-2BQ07-5AJ0	WinCC/Powerp RT 102400/153600 V7.5.2 DL
6AV6371-2BQ07-5AX0	WinCC/Powerp RT 102400/153600 V7.5 SP2
6AV6371-2BQ17-5AJ0	WinCC/Powerp RC 102400/153600 V7.5SP2 DL
6AV6371-2BQ17-5AX0	WinCC/Powerp RC 102400/153600 V7.5 SP2
6AV6371-2BR07-5AJ0	WinCC/Powerp RT 153600/262144 V7.5.2 DL
6AV6371-2BR07-5AX0	WinCC/Powerp RT 153600/262144 V7.5 SP2
6AV6371-2BR17-5AJ0	WinCC/Powerp RC 153600/262144 V7.5SP2 DL
6AV6371-2BR17-5AX0	WinCC/Powerp RC 153600/262144 V7.5 SP2
6AV6371-2BS07-5AJ0	WinCC/Powerp RT 262144/500000 V7.5.2 DL
6AV6371-2BS17-5AJ0	WinCC/Powerp RC 262144/500000 V7.5.2 DL

6AV6381-2AA07-5AK3	WinCC UPGR RT V7.2/7.3 -> RT V7.5 SP2 DL
6AV6381-2AA07-5AK4	WinCC UPGR RT V7.4 -> RT V7.5 SP2 DL
6AV6381-2AA07-5AV3	WinCC UG RT V7.2/7.3-> RT V7.5 SP2 Asia
6AV6381-2AA07-5AV4	WinCC Upgr RT V7.4-> RT V7.5 SP2 Asia
6AV6381-2AA07-5AX3	WinCC Upgr RT V7.2/7.3 -> RT V7.5 SP2
6AV6381-2AA07-5AX4	WinCC Upgr RT V7.4 -> RT V7.5 SP2
6AV6381-2AB07-5AK3	WinCC UPGR RC V7.2/7.3 -> RC V7.5 SP2 DL
6AV6381-2AB07-5AK4	WinCC UPGR RC V7.4 -> RC V7.5 SP2 DL
6AV6381-2AB07-5AV3	WinCC UG RC V7.2/7.3-> RC V7.5 SP2 Asia
6AV6381-2AB07-5AV4	WinCC Upgr RC V7.4-> RC V7.5 SP2 Asia
6AV6381-2AB07-5AX3	WinCC Upgr RC V7.2/7.3 -> RC V7.5 SP2
6AV6381-2AB07-5AX4	WinCC Upgr RC V7.4 -> RC V7.5 SP2
6AV6381-2CA07-5AK3	WinCC UG RT Cl. V7.2/7.3 -> V7.5 SP2 DL
6AV6381-2CA07-5AK4	WinCC UPGR RT Cl. V7.4 -> V7.5 SP2 DL
6AV6381-2CA07-5AV3	WinCC UG RT Cl. V7.2/7.3->V7.5 SP2 Asia
6AV6381-2CA07-5AV4	WinCC Upgr RT Cl. V7.4 ->V7.5 SP2 Asia
6AV6381-2CA07-5AX3	WinCC Upgr RT Cl. V7.2/7.3 -> V7.5 SP2
6AV6381-2CA07-5AX4	WinCC Upgr RT Cl. V7.4 -> V7.5 SP2
6AV6381-2CB07-5AK3	WinCC UPGR RC Cl. V7.2/7.3-> V7.5 SP2 DL
6AV6381-2CB07-5AK4	WinCC UPGR RC Cl. V7.4-> V7.5 SP2 DL
6AV6381-2CB07-5AV3	WinCC UG RC Cl. V7.2/7.3->V7.5 SP2 Asia
6AV6381-2CB07-5AV4	WinCC Upgr RC Cl. V7.4 ->V7.5 SP2 Asia
6AV6381-2CB07-5AX3	WinCC Upgr RC Cl. V7.2/7.3 -> V7.5 SP2
6AV6381-2CB07-5AX4	WinCC Upgr RC Cl. V7.4 -> V7.5 SP2

6AV6382-2AA07-5AV0	WinCC Package RT Client, V7.5 SP2 Asia
6AV6382-2AA07-5AX0	WinCC Package RT Client, V7.5 SP2
6AV6382-2CA07-5AV0	WinCC Package RT 128, V7.5 SP2 Asia
6AV6382-2CA07-5AX0	WinCC Package RT 128, V7.5 SP2
6AV6382-2DA07-5AV0	WinCC Package RT 512, V7.5 SP2 Asia
6AV6382-2DA07-5AX0	WinCC Package RT 512, V7.5 SP2
6AV6382-2EA07-5AV0	WinCC Package RT 2048, V7.5 SP2 Asia
6AV6382-2EA07-5AX0	WinCC Package RT 2048, V7.5 SP2
6AV6382-2FA07-5AV0	WinCC Package RT 65536, V7.5 SP2 Asia
6AV6382-2FA07-5AX0	WinCC Package RT 65536, V7.5 SP2
6AV6382-2HA07-5AV0	WinCC Package RT 8192, V7.5 SP2 Asia
6AV6382-2HA07-5AX0	WinCC Package RT 8192, V7.5 SP2

6AV6371-1DQ17-5AX0	WinCC/Archive V7.5 SP2, 1500 Arch. Tags
6AV6371-1DQ17-5BX0	WinCC/Archive V7.5 SP2, 5000 Arch. Tags
6AV6371-1DQ17-5CX0	WinCC/Archive V7.5 SP2, 10000 Arch. Tags
6AV6371-1DQ17-5EX0	WinCC/Archive V7.5 SP2, 30000 Arch. Tags
6AV6371-1HQ17-5AX0	WinCC/Arch. V7.5 SP2, 1500 Arch.Tags DL
6AV6371-1HQ17-5BX0	WinCC/Arch. V7.5 SP2, 5000 Arch.Tags DL
6AV6371-1HQ17-5CX0	WinCC/Arch. V7.5 SP2, 10000 Arch.Tags DL
6AV6371-1HQ17-5EX0	WinCC/Arch. V7.5 SP2, 30000 Arch.Tags DL
6AV6371-1CA07-5AX0	WinCC/Server V7.5 SP2
6AV6371-1CB07-5AX0	WinCC/User Archives V7.5 SP2
6AV6371-1CC07-5AX0	SIMATIC WinCC/ODK V7.5 SP2
6AV6371-1CF07-5AX0	WINCC/Redundancy V7.5 SP2
6AV6371-1GC07-5AX0	SIMATIC WinCC/ODK V7.5 SP2 DL
6AV6371-1HA07-5AX0	WinCC/Server V7.5 SP2 DL
6AV6371-1HB07-5AX0	WinCC/User Archives V7.5 SP2 DL
6AV6371-1HF07-5AX0	WinCC/Redundancy V7.5 SP2 DL
6AV6362-5AA07-5AH0	WinCC/Cloud Connect V7.5 DL
6AV6362-5AA07-5BB0	WinCC/Cloud Connect V7.5
6AV6371-1DR07-5AX0	WinCC/Connectivity Pack V7.5 SP2
6AV6371-1DR17-5AX0	WinCC/Connectivity Station V7.5 SP2
6AV6371-1HR07-5AX0	WinCC/Connectivity Pack V7.5 SP2 DL
6AV6371-1HR17-5AX0	WinCC/Connectivity Station V7.5 SP2 DL

6AV6371-1DV07-5AX0	WinCC/Audit RT V7.5 SP2
6AV6371-1DV07-5BX3	WinCC/Audit RT Upgr V7.2/7.3 -> V7.5 SP2
6AV6371-1DV07-5BX4	WinCC/Audit RT Upgr V7.4 -> V7.5 SP2
6AV6371-1DV17-5AX0	WinCC/Audit RC V7.5 SP2
6AV6371-1DV17-5BX3	WinCC/Audit RC Upgr V7.2/7.3 -> V7.5 SP2
6AV6371-1DV17-5BX4	WinCC/Audit RC Upgr V7.4 -> V7.5 SP2
6AV6371-1DV27-5AX0	WinCC/Change-Control V7.5 SP2
6AV6371-1HV07-5AX0	WinCC/Audit RT V7.5 SP2 DL
6AV6371-1HV17-5AX0	WinCC/Audit RC V7.5 SP2 DL

6AV6371-1HV27-5AX0	WinCC/Change-Control V7.5 SP2 DL
6AV6371-1KG07-5AX4	WinCC/ProAgent Upgr V7.4 -> V7.5 SP2 DL
6AV6371-1KV07-5BX4	WinCC/Audit RT Upgr V7.4 -> V7.5 SP2 DL
6AV6371-1KV17-5BX4	WinCC/Audit RC Upgr V7.4 -> V7.5 SP2 DL
6AV6362-4AA07-5AA0	WinCC/IDB, Basic Pckg V7.5 SP2
6AV6362-4AA07-5AE0	WinCC/IDB, Upgr V7.2/7.3 -> V7.5 SP2
6AV6362-4AA07-5AE1	WinCC/IDB, Upgr V7.4 -> V7.5 SP2
6AV6362-4AA07-5AH0	WinCC/IDB, Basic Pckg V7.5 SP2 DL
6AV6362-4AA07-5AK0	WinCC/IDB, Upgr V7.2/7.3 -> V7.5 SP2 DL
6AV6362-4AA07-5AK1	WinCC/IDB, Upgr V7.4 -> V7.5 SP2 DL
6AV6371-1HG07-5AX0	WinCC/ProAgent V7.5 SP2 DL
6AV6371-1DG07-5AX0	WinCC/ProAgent V7.5 SP2
6AV6371-1DG07-5AX3	WinCC/ProAgent Upgr V7.2/7.3 -> V7.5 SP2
6AV6371-1DG07-5AX4	WinCC/ProAgent Upgr V7.4 -> V7.5 SP2
6AV6372-1DC07-5AX0	WinCC/Calender Scheduler V7.5 SP2
6AV6372-1DC07-5AX4	WinCC/Calendar Opt Upgr V7.4 -> V7.5 SP2
6AV6372-1DD07-5AX0	WinCC/Event Notifier V7.5 SP2
6AV6372-1HC07-5AX0	WinCC/Calendar Scheduler V7.5 SP2 DL
6AV6372-1HD07-5AX0	WinCC/Event Notifier V7.5 SP2 DL
6AV6372-1KC07-5AX4	WinCC/Calendar Opt Upgr V7.4->V7.5.1 DL
6AV6372-2BJ07-5BA0	WinCC/SES V7.5 SP2, Extension 5 Units
6AV6372-2BJ17-5BA0	WinCC/SES V7.5 Ext. 5 Units Upgr V7.3
6AV6372-2BJ17-5BA1	WinCC/SES V7.5 Ext. 5 Units Upgr V7.4
6AV6372-2DG07-5AA0	WinCC/PerfMon V7.5 SP2 Basic Pack
6AV6372-2DG07-5AX3	WinCC/PerfMon UG V7.2/7.3-> V7.5 SP2
6AV6372-2DG07-5AX4	WinCC/Perf. Mon. Upgr V7.4-> V7.5 SP2
6AV6372-2DJ07-5AA0	WinCC/SES V7.5 SP2, Basic Pack
6AV6372-2DJ17-5AA0	WinCC/SES V7.5 SP2, Basic Pack Upgr
6AV6372-2DJ17-5AA1	WinCC/SES V7.5 SP2, Basic Pack Upgr
6AV6372-2HG07-5AA0	WinCC/PerfMon V7.5 SP2 Basic Pack. DL
6AV6372-2HJ07-5AA0	WinCC/SES V7.5 SP2, Basic Pack DL
6AV6372-2HJ17-5AA0	WinCC/SES V7.5 SP2, Basic Pack Upgr DL
6AV6372-2HJ17-5AA1	WinCC/SES V7.5 SP2, Basic Pack Upgr DL
6AV6372-2JJ07-5BA0	WinCC/SES V7.5 SP2, Extension 5 Units DL
6AV6372-2JJ17-5BA0	WinCC/SES V7.5 Ext. 5 Units Upgr V7.3 DL
6AV6372-2JJ17-5BA1	WinCC/SES V7.5 Ext. 5 Units Upgr V7.4 DL
6AV6372-2KG07-5AX3	WinCC/PerfMon UG V7.2/7.3-> V7.5 SP2 DL
6AV6372-2KG07-5AX4	WinCC/Perf. Mon. Upgr V7.4-> V7.5 SP2 DL