

Compatibility list of the Windows operating systems and SIMATIC optional packages with versions of the STEP 7 basic package

Legend: X = combination permitted
- = combination not permitted
(-) = combination not tested

Notes:

- This list (possibly a more up to date version) is available on the Internet at: <http://support.automation.siemens.com/WW/view/en/18734363>
- All statements regarding compatibility relate to the installation and combined running of the software on the same PC/programming device
- **Statements regarding compatibility with a STEP 7 version also apply to the service packs for this version unless restrictions are explicitly stated.** (Example: The statements regarding compatibility with STEP 7 V5.5 also apply to STEP 7 V5.5+SP1, ...)
- **Statements regarding compatibility with an S7 optional package also apply to the service packs for this version unless restrictions are explicitly stated.** (Example: The statements regarding compatibility with CFC V7.1 also apply to CFC V7.1+SP1, ...)
- The Microsoft Windows operating systems are abbreviated in the table below as follows:
 - Win XP SP2 Microsoft Windows XP Professional Edition + Service Pack 2
 - Win XP SP3 Microsoft Windows XP Professional Edition + Service Pack 3
 - Win 2003 SP2 Microsoft Windows Server 2003 + Service Pack 2 Standard Edition with or without R2 as Workstation
 - Vista Microsoft Windows Vista 32bit Ultimate or Business
 - Vista SP1 Microsoft Windows Vista 32bit + Service Pack 1 Ultimate or Business
 - Win 7 Microsoft Windows 7 32bit Ultimate or Professional
 - Win 7 SP1 Microsoft Windows 7 32bit + Service Pack 1 Ultimate or Professional
 - Win 7 (64) Microsoft Windows 7 64bit Ultimate or Professional
 - Win 7 SP1 (64) Microsoft Windows 7 64bit Ultimate or Professional
 - Win 2008 R2 (64) Microsoft Windows Server 2008 R2 64bit Std. Edition
 - Win 2008 R2 SP1 (64) Microsoft Windows Server 2008 R2 64bit + Service Pack 1 Std. Edition
 - Win 2012 R2 (64) Microsoft Windows Server 2012 R2 64bit StdE
 - Win 2016 (64) Microsoft Windows Server 2016 64bit
 - Win 2019 (64) Microsoft Windows Server 2019 64bit
 - Win 10 (64) Microsoft Windows 10 64bit Pro, Enterprise, Enterprise 2019 LTSC or IoT Enterprise 2019 LTSC

STEP 7 Basic Packages																	
Product Name	Version	Order Number	Win XP SP2	Win XP SP3	Win 2003 SP2	Vista	Vista SP1	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
STEP 7	V5.6 SP2	6ES7 810-4CC11-0YA5	-	-	-	-	-	-	-	-	X	-	X	X	X	X	X
STEP 7	V5.6 SP1	6ES7 810-4CC11-0YA5	-	-	-	-	-	-	-	-	X	-	X	X	X	-	X
STEP 7	V5.6	6ES7 810-4CC11-0YA5	-	-	-	-	-	-	(-)	-	X	-	X	X	X	-	X
STEP 7	V5.5 SP4	6ES7 810-4CC10-0YA5	-	(-)	X1)	-	-	(-)	X	X	X	X	X	-	-	-	-
STEP 7	V5.5 SP3	6ES7 810-4CC10-0YA5	X	X	X1)	-	-	X	X	X	X	X	X	-	-	-	-
STEP 7	V5.5 SP2	6ES7 810-4CC10-0YA5	X	X	X1)	-	-	X	X	X	X	X	X	-	-	-	-
STEP 7	V5.5 SP1	6ES7 810-4CC10-0YA5	X	X	X1)	-	-	X	X	X	X	X	X	-	-	-	-
STEP 7	V5.5	6ES7 810-4CC10-0YA5	X	X	X	(-)	(-)	X	-	-	-	-	-	-	-	-	-
STEP 7 Professional	2017 SR2	6ES7 810-5CC13-0YA5	-	-	-	-	-	-	-	-	X	-	X	X	X	X	X
STEP 7 Professional	2017 SR1	6ES7 810-5CC12-0YA5	-	-	-	-	-	-	-	-	X	-	X	X	X	-	X
STEP 7 Professional	2017	6ES7 810-5CC12-0YA5	-	-	-	-	-	-	(-)	-	X	-	X	X	X	-	X
STEP 7 Professional	2010 SR3	6ES7 810-5CC11-0YA5	X	X	X1)	-	-	X	X	X	X	X	X	-	-	-	-
STEP 7 Professional	2010 SR2	6ES7 810-5CC11-0YA5	X	X	X1)	-	-	X	X	X	X	X	X	-	-	-	-
STEP 7 Professional	2010 SR1	6ES7 810-5CC11-0YA5	X	X	X1)	-	-	X	X	X	X	X	X	-	-	-	-
STEP 7 Professional	2010	6ES7 810-5CC11-0YA5	X	X	X	(-)	(-)	X	-	-	-	-	-	-	-	-	-

Note: SIMATIC M7 is released only for operation with Windows 2000 SP4 or Windows XP SP1/2

¹⁾ only for Windows Server 2003 R2 SP2

Automation License Manager			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
Automation License Manager	V6.0	----	-	-	X	X	X	X	X	X	X	X	X	X	X	X
Automation License Manager	V5.3	----	X	X	X	X	X	X	X	X	X	X	X	X ¹⁾	(-)	X ¹⁾
Automation License Manager	V5.2	----	X	X	X	X	X	X	X	X	X	X	X	-	-	-
Automation License Manager	V5.1	----	X	X	X	X	X	X	X	X	X	X	-	-	-	-
Automation License Manager	V5.0	----	X	X	X	(-)	-	-	-	-	-	-	-	-	-	-
Automation License Manager	V4.0	----	(-)	(-)	(-)	(-)	-	-	-	-	-	-	-	-	-	-
Automation License Manager	V3.0	----	(-)	(-)	(-)	(-)	-	-	-	-	-	-	-	-	-	-
Automation License Manager	V2.2	----	(-)	(-)	(-)	(-)	-	-	-	-	-	-	-	-	-	-

Note: The current Automation License Manager is part of the STEP 7 system setup

¹⁾ only for Automation License Manager V5.3 SP4 Update 3 and higher

CFC			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
CFC	V9.0	6ES7 658-1EX58-0YA5	-	-	-	X	-	X	-	X	X	X	X	-	-	X
CFC	V8.2	6ES7 658-1EX28-2YA5	X	X	X	X	X	X	X	X	X	X	-	-	-	-
CFC	V8.0	6ES7 658-1EX08-2YA5	X	X	X	X	X	X	X	X	X	X	-	-	-	-
CFC	V7.1	6ES7 658-1EX17-2YA5	X	X	X ²⁾	(-)	-	-	-	-	-	-	-	-	-	-
CFC	V7.0	6ES7 658-1EX07-2YA5	X ¹⁾	X ¹⁾	-	-	-	-	-	-	-	-	-	-	-	-

¹⁾ only as of CFC V7.0+SP1 or higher

²⁾ only as of CFC V7.1+SP2 or higher

D7-SYS for SIMATIC TDC, FM 458, T400, SIMADYN D			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
D7-SYS	V9.0 ⁴⁾	6ES7 852-0CC06-0YA5	-	-	-	-	-	X	-	X	X	X	X	X	-	X
D7-SYS	V8.2	6ES7 852-0CC05-0YA5	-	-	-	X	-	X	-	X	X	X	X	-	-	-
D7-SYS	V8.1	6ES7 852-0CC04-0YA5	-	-	X	X	X	X	-	-	-	-	-	-	-	-
D7-SYS	V8.0 ³⁾	6ES7 852-0CC03-0YA5	X	X	X	X	X	X	-	-	-	-	-	-	-	-
D7-SYS	V7.1 ²⁾	6ES7 852-0CC02-0YA5	X	X	-	-	-	-	-	-	-	-	-	-	-	-
D7-SYS	V7.0 ¹⁾	6ES7 852-0CC01-0YA5	-	-	-	-	-	-	-	-	-	-	-	-	-	-

¹⁾ contains CFC V7.0 + SP1, SFC V7.0 + SP1 minimum requirements: STEP 7 V5.4 + SP3 or higher

²⁾ contains CFC V7.1, SFC V7.1; minimum requirements: STEP 7 V5.4 + SP4 or higher

³⁾ contains CFC V8.0, SFC V8.0; minimum requirements: STEP 7 V5.5 + SP2 or higher

⁴⁾ contains CFC V9.0, SFC V9.0; minimum requirements: STEP 7 V5.6 or higher

DOCPRO			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
DOCPRO	V5.4	6ES7 803-0CC03-0YA5	X	X	X ¹⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	-	-	-	-
DOCPRO	V5.1+SP2	6ES7 803-0CC02-0YE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-

¹⁾ only as of DOCPRO V5.4+SP1 or higher

²⁾ only as of DOCPRO V5.4+SP2 or higher

Modular PID CONTROL			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
Modular PID Control (Tool)	V5.1.3	6ES7 830-1AA11-0YX0	-	-	-	-	-	-	-	-	X	X	X	X	(-)	X
Modular PID Control (Tool)	V5.1.2	6ES7 830-1AA11-0YX0	X	X	X	X	X	X	(-)	(-)	X	(-)	-	-	-	-
Modular PID Control (Tool)	V5.1.1	6ES7 830-1AA11-0YX0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
Modular PID Control (Tool)	V5.1	6ES7 830-1AA11-0YX0	(-)	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-
Modular PID Control (Tool)	V5.0	6ES7 830-1AA10-0YX0	-	-	-	-	-	-	-	-	-	-	-	-	-	-

Standard PID Control			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
Standard PID Control (Tool)	V5.2.4	6ES7 830-2AA22-0YX0	-	-	--	-	-	-	-	-	X	X	X	X	(-)	X
Standard PID Control (Tool)	V5.2.3	6ES7 830-2AA22-0YX0	X	X	X	X	X	X	(-)	(-)	X	(-)	-	-	-	-
Standard PID Control (Tool)	V5.2.2 V5.2.1	6ES7 830-2AA22-0YX0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
Standard PID Control (Tool)	V5.2	6ES7 830-2AA22-0YX0	(-)	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-
Standard PID Control (Tool)	V5.1	6ES7 830-2AA21-0YX0	(-)	-	-	-	-	-	-	-	-	-	-	-	-	-

PID Self-Tuner			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
PID Self-Tuner (FBs)	V5.1.3	6ES7 860-4AA01-0YX0	-	-	-	-	-	-	-	-	X	X	X	X	(-)	X
PID Self-Tuner (FBs)	V5.1.2	6ES7 860-4AA01-0YX0	X	X	X	X	X	X	(-)	(-)	X	(-)	-	-	-	-
PID Self-Tuner (FBs)	V5.1	6ES7 860-4AA01-0YX0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
PID Self-Tuner (FBs)	V5.0.1	6ES7 860-4AA01-0YX0	-	-	-	-	-	-	-	-	-	-	-	-	-	-

PC-Adapter USB			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
PC-Adapter USB A2 USB-Adapter	USB V2.0	6GK1 571-0BA00-0AA0	X	X	X	X	X	X	X	X	X	X	X	X	X	X
PC-Adapter USB	only HW ¹⁾	6ES7 972-0CB20-0XA0	X	X	X	X	X	X	X	X	X	X	X	X	X	X
PC-Adapter USB	V2.0	6ES7 972-0CB20-0XA0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PC-Adapter USB	V1.2	6ES7 972-0CB20-0XA0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PC-Adapter USB	V1.1	6ES7 972-0CB20-0XA0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PC-Adapter USB A2 USB-Adapter	USB V2.0	6GK1 571-0BA00-0AA0	X	X	X	X	X	X	X	X	X	X	X	X	X	X

¹⁾The functionality of PC-Adapter USB is integrated in STEP 7 V5.5 and V5.6. For this reason, drivers no longer have to be installed in order to operate the PC-Adapter USB.

S7-Distributed Safety			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
S7-Distributed Safety	V5.4	6ES7 833-1FC02-0YA5	X ¹⁾	X ¹⁾	X ²⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	(-)	X ⁴⁾

¹⁾ only as of S7-Distributed Safety V5.4+SP5 or higher

²⁾ only as of S7-Distributed Safety V5.4+SP5 or higher and S7-F Configuration Pack V5.5+SP7 or higher

³⁾ only as of S7-Distributed Safety V5.4+SP5+Upd1 or higher and S7-F Configuration Pack V5.5+SP9 or higher

⁴⁾ only as of S7-Distributed Safety V5.4+SP5+Upd2 or higher and S7-F Configuration Pack V5.5+SP13 or higher

S7-F Systems			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
S7-F Systems	V6.2	6ES7 833-4CC26-0YA5	-	-	-	X	-	X	-	X	X	X	X	X ²⁾	X ²⁾	X
S7-F Systems	V6.1+SP2	6ES7 833-1CC02-0YA5	X	(-)	(-)	X	-	X	(-)	X	X	X	-	-		-
S7-F Systems	V6.1	6ES7 833-1CC02-0YA5	X	X	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	-	-		-
S7-F Systems	V6.0	6ES7 833-1CC01-0YA5	X	-	-	-	-	-	-	-	-	-	-	-		-

Note: S7-F Systems requires CFC

¹⁾ only as of S7-F Systems V6.1+SP1

²⁾ only as of S7-F Systems V6.2+Update 1

S7-GRAPH			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
S7-GRAPH	V5.6 SP2	6ES7 811-0CC07-0YA5	-	-	-	-	-	X	-	X	X	X	X	X	X	X
S7-GRAPH	V5.6	6ES7 811-0CC07-0YA5	-	-	-	-	-	X	-	X	X	X	X	X	(-)	X
S7-GRAPH	V5.3	6ES7 811-0CC06-0YA5	X ²⁾	X ¹⁾	X ²⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	-	-	-	-		-

¹⁾ only as of S7-GRAPH V5.3+SP4 or higher

²⁾ only as of S7-GRAPH V5.3+SP6 or higher

³⁾ only as of S7-GRAPH V5.3+SP7 or higher

S7-HiGraph			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
S7-HiGraph	V5.3	6ES7 811-3CC05-0YA5	X ¹⁾	X ¹⁾	-	-	-	-	-	-	-	-	-	-	-	-
S7-HiGraph	V5.2	6ES7 811-3CC04-0YE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-

¹⁾ only as of S7-HiGraph V5.3+SP1 or higher

S7-PCT			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 R2 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
S7-PCT	V3.5	----	-	-	-	(-)	-	X	-	X	X	X	X	X	X	X
S7-PCT	V3.4	----	(-)	(-)	X	X	X	X	X	X	X	X	X	X	-	X
S7-PCT	V3.3	----	(-)	(-)	X	X	X	X	X	X	X	X	X	X	-	X
S7-PCT	V3.2	----	X	X	X	X	X	X	X	X	X	X	-	-	-	-
S7-PCT	V3.1	----	X	X	X	X	X	X	X	X	X	X	-	-	-	-
S7-PCT	V3.0	----	X ³⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	-	-	-	-
S7-PCT	V2.3	----	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	-	-	-	-
S7-PCT	V2.2	----	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	-	-	-	-
S7-PCT	V2.1	----	X	X	X	-	-	-	-	-	-	-	-	-	-	-
S7-PCT	V2.0	----	(-)	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-

Note: The respective current S7-PCT is a component of the general setup of STEP 7

1) only as of STEP 7 V5.5+SP1

2) only as of STEP 7 V5.5+SP2

3) only as of STEP 7 V5.5+SP3

S7-PDIAG			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
S7-PDIAG	V5.6	6ES7 840-0CC05-0YA5	-	-	-	-	-	-	-	-	X	X	X	X	X	X
S7-PDIAG	V5.3	6ES7 840-0CC04-0YA5	X ¹⁾	X ¹⁾	X ¹⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	-	-	-	-	-	-
S7-PDIAG	V5.1	6ES7 840-0CC03-0YE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-

1) only as of S7-PDIAG V5.3+SP5 or higher

2) only as of S7-PDIAG V5.3+SP6 or higher

S7-PLCSIM			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
S7-PLCSIM ¹⁾	V5.4	6ES7 841-0CC05-0YA5	X ³⁾	X ¹⁾	X ⁴⁾	X ⁵⁾	X ⁵⁾	X ⁵⁾	X ⁵⁾	X ⁵⁾	X ⁶⁾	X ⁶⁾	X ⁶⁾	X ⁶⁾	X ⁶⁾	X ⁶⁾
S7-PLCSIM	V5.3	6ES7 841-0CC04-0YA5	X	X	-	-	-	-	-	-	-	-	-	-	-	-

1) only as of STEP 7 V5.4+SP1 or higher

3) only as of S7-PLCSIM V5.4+SP2 or higher

4) only as of S7-PLCSIM V5.4+SP4 or higher

6) only as of S7-PLCSIM V5.4+SP5 or higher

6) only as of S7-PLCSIM V5.4+SP8 or higher

S7-SCL			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
S7-SCL	V5.6	6ES7 811-1CC06-0YA5	-	-	-	-	-	(-)	(-)	(-)	X	X	X	X	X	X
S7-SCL	V5.3	6ES7 811-1CC05-0YA5	X ²⁾	X ¹⁾	X ²⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	X ³⁾	-	-	-	-

¹⁾ only as of S7-SCL V5.3+SP3 or higher

²⁾ only as of S7-SCL V5.3+SP5 or higher

³⁾ only as of S7-SCL V5.3+SP6 or higher

S7-Technology			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
S7-Technology	V4.2+SP4	6ES7 864-1CC42-0YA5	-	-	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	-	-	X	-	-	-	-	-
S7-Technology	V4.2+SP3	6ES7 864-1CC42-0YA5	X ¹⁾	-	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	-	-	X	-	-	-	-	-
S7-Technology	V4.2+SP2	6ES7 864-1CC42-0YA5	X ¹⁾	-	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	-	-	X	-	-	-	-	-
S7-Technology	V4.2+SP1	6ES7 864-1CC42-0YA5	X ¹⁾	-	X ¹⁾	X ¹⁾	-	-	-	-	-	-	-	-	-	-
S7-Technology	V4.2	6ES7 864-1CC42-0YA5	X	-	(-)	-	-	-	-	-	-	-	-	-	-	-
S7-Technology	V4.1	6ES7 864-1CC41-0YX0	X	-	-	-	-	-	-	-	-	-	-	-	-	-
S7-Technology	V3.0	6ES7 864-1CC30-0YX0	(-)	-	-	-	-	-	-	-	-	-	-	-	-	-
S7-Technology	V2.0	6ES7 864-1CC20-0YX0	-	-	-	-	-	-	-	-	-	-	-	-	-	-

Note: S7-Technology cannot be installed alongside SIMOTION SCOUT or Drive ES Basic with the component STARTER on one PC/programming device.

For the function "Drive Control Chart (DCC)", S7 technology contains certain versions of the CFC product and cannot be combined with other versions of CFC.

¹⁾ only as of STEP 7 V5.5+SP2 or higher

SIMATIC iMap			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
SIMATIC iMap	V3.0+SP3V3.0+SP2	6ES7 820-0CC04-0YA5	X	X	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	-	-	-	-
SIMATIC iMap	V3.0	6ES7 820-0CC04-0YA5	X ¹⁾	X ¹⁾	-	-	-	-	-	-	-	-	-	-	-	-
SIMATIC iMap	V2.0+SP2	6ES7 820-0CC03-0YX0	-	-	-	-	-	-	-	-	-	-	-	-	-	-

Note: to run SIMATIC iMap, the SIMATIC iMap STEP 7-Add-on suitable for the STEP 7 Version must be installed. This ships on the STEP 7 DVD or can be obtained from the Internet.

¹⁾ only as of SIMATIC iMap V3.0+SP1 or higher

²⁾ only as of SIMATIC iMap V3.0+SP3 or higher

SIMATIC Logon			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
SIMATIC Logon	V1.6	6ES7 658-7BX61-0YA0	-	-	-	X	-	X	-	X	X	X	X	-	-	X
SIMATIC Logon	V1.5+SP2	6ES7 658-7BX51-0YA0	X	X	X	X	X	X	X	X	X	X	-	-	-	-
SIMATIC Logon	V1.5	6ES7 658-7BX41-2YA0	X	X	X	X	X	X	X	(-)	(-)	-	-	-	-	
SIMATIC Logon	V1.4+SP4	6ES7 658-7BX41-2YA0	-	-	-	-	X	X	X	(-)	(-)	-	-	-	-	
SIMATIC Logon	V1.4	6ES7 658-7BX41-2YA0	X ¹⁾	X ¹⁾	X ²⁾	X ²⁾	-	-	-	-	-	-	-	-	-	-

Note: With STEP 7 as of V5.4+SP3, you should use SIMATIC Logon V1.4+SP1 or higher.

¹⁾ only as of SIMATIC Logon V1.4+SP1 or higher

²⁾ only as of SIMATIC Logon V1.4+SP3 or higher

SIMATIC Maintenance Station			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
SIMATIC Maintenance Station	2009+SP3(V2.0.3)	6ES7 840-0WD01-0YA0	X ³⁾	X ²⁾³⁾	(-)	X ³⁾	(-)	X ³⁾	(-)	X ³⁾	X	X	(-)	-	-	-
SIMATIC Maintenance Station	2009+SP2(V2.0.2)	6ES7 840-0WD01-0YA0	X	X ²⁾	X	(-)	(-)	X	(-)	X	X	X	-	-	-	-
SIMATIC Maintenance Station	2009+SP1(V2.0.1)	6ES7 840-0WD01-0YA0	X	X ²⁾	X	(-)	-	-	-	-	-	-	-	-	-	-
SIMATIC Maintenance Station	2009 (V2.0)	6ES7 840-0WD01-0YA0	X	X	-	-	-	-	-	-	-	-	-	-	-	-
SIMATIC Maintenance Station	2007 (V1.0)	6ES7 840-0WD00-0YA0	(-)	X ¹⁾	-	-	-	-	-	-	-	-	-	-	-	-

¹⁾ only as of SIMATIC Maintenance Station 2007+SP2 or higher

²⁾ only Windows Server 2003 R2 SP2

³⁾ only STEP 7 V5.5+SP2 or SP3

SIMATIC NET			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
SIMATIC NET PC Software	V16		-	-	-	-	-	X	-	-	X	-	X	X	X	X
SIMATIC NET PC Software	V15		-	-	-	-	-	X	-	X	X	X	X	X	(-)	X
SIMATIC NET PC Software	V14		-	-	X	X	X	X	X	X	X	X	(-)	-	-	(-)
SIMATIC NET PC Software	V8.2		-	-	X	X	X	X	X	X	X	X	-	-	-	-
SIMATIC NET PC Software	V8.0		-	-	X	-	-	-	-	-	-	-	-	-	-	-
SIMATIC NET PC Software	2008 (V7.1)		X	X	-	-	-	-	-	-	-	-	-	-	-	-

SIMATIC PDM			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
SIMATIC PDM	V9.1 ³⁾	6ES7 658-3AB68-0YA5	-	-	-	X	-	X	-	X	X	X	X	X	(-)	X
SIMATIC PDM	V9.0 ³⁾	6ES7 658-3AB58-0YA5	-	-	-	X	-	X	-	X	X	X	(-)	-	-	X
SIMATIC PDM	V8.2 ³⁾	6ES7 658-3AB28-0YA5	-	-	-	X	-	X	-	X	-	-	-	-	-	-
SIMATIC PDM	V8.1.1	6ES7 658-3AB18-0YA5	X	X ²⁾	-	X	-	X	-	X	-	-	-	-	-	-
SIMATIC PDM	V8.1	6ES7 658-3AB18-0YA5	X	X ²⁾	-	X	-	X	-	X	-	-	-	-	-	-
SIMATIC PDM	V8.0.2	6ES7 658-3MD08-0YA5	X	X ²⁾	-	X	-	X	-	X	-	-	-	-	-	-
SIMATIC PDM	V8.0.1	6ES7 658-3MD08-0YA5	X	X ²⁾	-	X	-	X	-	X	-	-	-	-	-	-
SIMATIC PDM	V8.0	6ES7 658-3LD08-0YA5	X	X ²⁾	-	X	-	X	-	X	-	-	-	-	-	-
SIMATIC PDM	V6.1	6ES7 658-3AX16-0YA5	X	X ²⁾	-	-	-	-	-	-	-	-	-	-	-	-
SIMATIC PDM	V6.0	6ES7 658-3AX06-0YA5	X ¹⁾	-	-	-	-	-	-	-	-	-	-	-	-	-

¹⁾ only as of SIMATIC PDM V6.0+SP5

²⁾ only Windows Server 2003 R2 SP2

³⁾ only as of STEP 7 V5.5+SP4

SIMATIC Safety Matrix			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
SIMATIC Safety Matrix	V6.3	6ES7 833-1SM*3-0YA5	-	-	-	-	-	X	-	X	X	X	X	X	(-)	X
SIMATIC Safety Matrix	V6.2 + SP2	6ES7 833-1SM*2-0YA5	X	X	(-)	X	-	X	(-)	X	X	X	X	X	-	X
SIMATIC Safety Matrix	V6.2	6ES7 833-1SM*2-0YA5	X	X	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	-	-	-	-	-	-
SIMATIC Safety Matrix	V6.1	6ES7 833-1SM*1-0YA5	X	X	-	-	-	-	-	-	-	-	-	-	-	-

Note: SIMATIC Safety Matrix requires S7-F Systems and CFC

¹⁾ only as of SIMATIC Safety Matrix V6.2+SP1

SIMOTION SCOUT			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
SIMOTION Scout	V5.3 SP1	6AU1 810-1BA53-1XA0	-	-	-	-	-	-	-	-	X ⁴⁾	-	-	-	-	X ⁴⁾
SIMOTION Scout	V5.2 SP1	6AU1 810-1BA52-1XA0	-	-	-	-	-	-	-	-	X	-	-	-	-	X
SIMOTION Scout	V4.5 HF1	6AU1 810-1BA45-0XA0	-	-	-	X ³⁾	-	X ³⁾	-	-	X ³⁾	-	-	-	-	-
SIMOTION Scout	V4.3 SP1 HF12	6AU1 810-1BA43-1XA0	X ²⁾	-	X ²⁾	-	-	-	-	-	-	-	-	-	-	-
SIMOTION Scout	V4.3 SP1	6AU1 810-*BA43-1XA0	X ¹⁾	-	X ¹⁾	-	-	-	-	-	-	-	-	-	-	-
SIMOTION Scout	V4.2 SP1	6AU1 810-*BA42-1XA0	X ¹⁾	-	X ¹⁾	-	-	-	-	-	-	-	-	-	-	-

Further information on SIMOTION Scout compatibility can be found on the Internet at: <http://support.automation.siemens.com/WW/view/de/18857317>

¹⁾ only as of STEP 7 V5.5+SP1

²⁾ only as of STEP 7 V5.5+SP2+HF1

³⁾ only as of STEP 7 V5.5+SP4+HF11

⁴⁾ only as of STEP 7 V5.6+SP1

SINAUT Engineering			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
SINAUT Engineering	V5.5 SP3	6NH7 997-0CA55-0AA0	-	-	-	-	-	-	-	-	X	X	X	X	(-)	X
SINAUT Engineering	V5.5	6NH7 997-0CA55-0AA0	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	X ²⁾	(-)	(-)	-	-	-	-
SINAUT Engineering	V5.2	6NH7 997-0CA52-0AA0	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	X ¹⁾	-	-	-	-	-	-
SINAUT Engineering	V5.1	6NH7 997-0CA51-0AA0	X	X	(-)	-	-	-	-	-	-	-	-	-	-	-
SINAUT Engineering	V5.0	6NH7 997-0CA50-0AA0	X	X	(-)	-	-	-	-	-	-	-	-	-	-	-

¹⁾ only as of STEP 7 V5.5+SP1

²⁾ only as of STEP 7 V5.5+SP4

STARTER (drive commissioning tool)			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
STARTER	V5.3 HF3	6SL3 072-0AA00-0AG0	-	-	-	X	-	X	-	(-)	X	(-)	(-)	X	(-)	X
STARTER	V5.1 SP1	6SL3 072-0AA00-0AG0	-	-	-	X	-	X	-	X	X	X	X	X	-	X
STARTER	V4.5 SP1	6SL3 072-0AA00-0AG0	X	X	X	X	X	X	(-)	(-)	X	(-)	(-)	(-)	-	X
STARTER	V4.3 SP1	6SL3 072-0AA00-0AG0	X	X	X	(-)	-	-	-	-	-	-	-	-	-	-
STARTER	V4.2	6SL3 072-0AA00-0AG0	X	X	X	(-)	-	-	-	-	-	-	-	-	-	-
STARTER	V4.1	6SL3 072-0AA00-0AG0	X ¹⁾	(-)	-	-	-	-	-	-	-	-	-	-	-	-
STARTER	V4.0	6SL3 072-0AA00-0AG0	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-

¹⁾ only as of STARTER V4.1+SP2 or higher

STEP 7-Micro/WIN			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
STEP 7-Micro/WIN	V4.0	6ES7 810-2CC03-0YX0	X ¹⁾	-	X ²⁾	(-) ²⁾	X ²⁾	(-) ²⁾	-	-	(-) ₂₎	-	-	-	-	-
STEP 7-Micro/WIN	V3.2	6ES7 810-2BC02-0YX0	-	-	-	-	-	-	-	-	-	-	-	-	-	-

¹⁾ only as of STEP 7-Micro/WIN V4.0+SP7 or higher

²⁾ only as of STEP 7-Micro/WIN V4.0+SP9 or higher

Technological Functions			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
Easy Motion Control	V2.1.2	6ES7 864-0AC01-0YX0	-	-	X	X	X	X	-	-	X	-	-	-	-	X
Easy Motion Control	V2.1.1	6ES7 864-0AC01-0YX0	X	X	X	(-)	-	-	-	-	(-)	-	-	-	-	-
Easy Motion Control	V2.1	6ES7 864-0AC01-0YX0	(-)	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-
Easy Motion Control	V2.0	6ES7 864-0AC01-0YX0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
FM 350-1, 450-1 IF-CT1 Counter	V6.0.2	HW: 6ES7 350-1AH0*-0AE0 HW: 6ES7 450-1AP00-0AE0 HW: 6ES7 961-3AA00-0AC0	X	X	X	X	X	X	-	-	X	-	-	-	-	X
FM 350-1, 450-1 IF-CT1 Counter	V6.0.1	HW: 6ES7 350-1AH0*-0AE0 HW: 6ES7 450-1AP00-0AE0 HW: 6ES7 961-3AA00-0AC0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
FM 350-1, 450-1 IF-CT1 Counter	V6.0	HW: 6ES7 350-1AH0*-0AE0 HW: 6ES7 450-1AP00-0AE0 HW: 6ES7 961-3AA00-0AC0	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-
FM 350-1, 450-1 IF-CT1 Counter	V5.1	HW: 6ES7 350-1AH0*-0AE0 HW: 6ES7 450-1AP00-0AE0 HW: 6ES7 961-3AA00-0AC0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
FM 350-2 Counter	V6.0.2	HW: 6ES7 350-2AH00-0AE0	X	X	X	X	X	X	-	-	X	-	-	-	-	X
FM 350-2 Counter	V6.0.1	HW: 6ES7 350-2AH00-0AE0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
FM 350-2 Counter	V6.0	HW: 6ES7 350-2AH00-0AE0	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-
FM 350-2 Counter	V4.0.3	HW: 6ES7 350-2AH00-0AE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
FM 351, 451 Positioning	V6.0.2	HW: 6ES7 351-1AH0*-0AE0 HW: 6ES7 451-3AL00-0AE0	X	X	X	X	X	X	-	-	X	-	-	-	-	X
FM 351, 451 Positioning	V6.0.1	HW: 6ES7 351-1AH0*-0AE0 HW: 6ES7 451-3AL00-0AE0	X	X	X	X	-	-	-	-	-	-	-	-	-	-

Copyright © Siemens AG 2019
Subject to change

Siemens Aktiengesellschaft
A5E03013471-AH

Technological Functions			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
FM 351, 451 Positioning	V6.0	HW: 6ES7 351-1AH0*-0AE0 HW: 6ES7 451-3AL00-0AE0	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-
FM 351, 451 Positioning	V5.0.1	HW: 6ES7 351-1AH0*-0AE0 HW: 6ES7 451-3AL00-0AE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
FM 352, 452 Cam	V6.0.3	HW: 6ES7 352-1AH0*-0AE0 HW: 6ES7 452-1AH00-0AE0	X	X	X	X	X	X	-	-	X	-	-	-	-	X
FM 352, 452 Cam	V6.0.2	HW: 6ES7 352-1AH0*-0AE0 HW: 6ES7 452-1AH00-0AE0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
FM 352, 452 Cam	V6.0.1 V6.0	HW: 6ES7 352-1AH0*-0AE0 HW: 6ES7 452-1AH00-0AE0	X	X	-	-	-	-	-	-	-	-	-	-	-	-
FM 352, 452 Cam	V5.0.1	HW: 6ES7 352-1AH01-0AE0 HW: 6ES7 452-1AH00-0AE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
FM 352-5 Programming Environment	V1.2.3	HW: 6ES7 352-5AH1*-0AE0 HW: 6ES7 352-5AH0*-0AE0	X	X	X	X	X	X	-	-	X	-	-	-	-	X
FM 352-5 Programming Environment	V1.2.2	HW: 6ES7 352-5AH1*-0AE0 HW: 6ES7 352-5AH0*-0AE0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
FM 352-5 Programming Environment	V1.2.1	HW: 6ES7 352-5AH1*-0AE0 HW: 6ES7 352-5AH0*-0AE0	X	X	-	-	-	-	-	-	-	-	-	-	-	-
FM 352-5 Programming Environment	V1.2	HW: 6ES7 352-5AH1*-0AE0 HW: 6ES7 352-5AH0*-0AE0	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-
FM 352-5 Programming Environment	V1.1	HW: 6ES7 352-5AH1*-0AE0 HW: 6ES7 352-5AH0*-0AE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-

Technological Functions			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
FM 353 Step	V4.03.09	6ES7 353-1AH01-7AG0 HW: 6ES7 353-1AH01-0AE0	X	X	X	X	X	X	-	-	X	-	-	-	-	X
FM 353 Step	V4.03.07	6ES7 353-1AH01-7AG0 HW: 6ES7 353-1AH01-0AE0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
FM 353 Step	V4.03.05	6ES7 353-1AH01-7AG0 HW: 6ES7 353-1AH01-0AE0	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-
FM 353 Step	V4.03	6ES7 353-1AH01-7AG0 HW: 6ES7 353-1AH01-0AE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
FM 354 Servo	V4.03.09	6ES7 354-1AH01-7AG0 HW: 6ES7 354-1AH01-0AE0	X	X	X	X	X	X	-	-	X	-	-	-	-	X
FM 354 Servo	V4.03.07	6ES7 354-1AH01-7AG0 HW: 6ES7 354-1AH01-0AE0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
FM 354 Servo	V4.03.05	6ES7 354-1AH01-7AG0 HW: 6ES7 354-1AH01-0AE0	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-
FM 354 Servo	V4.03	6ES7 354-1AH01-7AG0 HW: 6ES7 354-1AH01-0AE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
FM 453 Step/Servo	V3.03.08	6ES7 453-3AH00-7AG0 HW: 6ES7 453-3AH00-0AE0	X	X	X	X	X	X	-	-	X	-	-	-	-	X
FM 453 Step/Servo	V3.03.07	6ES7 453-3AH00-7AG0 HW: 6ES7 453-3AH00-0AE0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
FM 453 Step/Servo	V3.03.06	6ES7 453-3AH00-7AG0 HW: 6ES7 453-3AH00-0AE0	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-
FM 453 Step/Servo	V3.03	6ES7 453-3AH00-7AG0 HW: 6ES7 453-3AH00-0AE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-

Technological Functions			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
FM 355, 455 PID Control	V6.1.2	HW: 6ES7 355-*VH*0-0AE0 HW: 6ES7 455-*VS00-0AE0	X	X	X	X	X	X	-	-	X	-	-	-	-	X
FM 355, 455 PID Control	V6.1.1	HW: 6ES7 355-*VH*0-0AE0 HW: 6ES7 455-*VS00-0AE0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
FM 355, 455 PID Control	V6.1	HW: 6ES7 355-*VH*0-0AE0 HW: 6ES7 455-*VS00-0AE0	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-
FM 355, 455 PID Control	V6.0	HW: 6ES7 355-*VH*0-0AE0 HW: 6ES7 455-*VS00-0AE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
FM 355, 455 PID Control	V5.0.1	HW: 6ES7 355-*VH*0-0AE0 HW: 6ES7 455-*VS00-0AE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
FM 355-2	V6.1.2	HW: 6ES7 355-2CH00-0AE0 HW: 6ES7 355-2SH00-0AE0	X	X	X	X	X	X	-	-	X	-	-	-	-	X
FM 355-2	V6.1.1	HW: 6ES7 355-2CH00-0AE0 HW: 6ES7 355-2SH00-0AE0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
FM 355-2	V6.1	HW: 6ES7 355-2CH00-0AE0 HW: 6ES7 355-2SH00-0AE0	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-
FM 355-2	V6.0	HW: 6ES7 355-2CH00-0AE0 HW: 6ES7 355-2SH00-0AE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
FM 355-2	V5.1	HW: 6ES7 355-2CH00-0AE0 HW: 6ES7 355-2SH00-0AE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
FM 357-2	V5.3.6	for HW: 6ES7 357-4AH03-3AE0 (L) 6ES7 357-4BH03-3AE0 (LX) 6ES7 357-4CH03-3AE0 (H)	X	X	X	X	-	-	-	-	-	-	-	-	-	-

Technological Functions			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
FM 357-2	V5.03	for HW: 6ES7 357-4AH03-3AE0 (L) 6ES7 357-4BH03-3AE0 (LX) 6ES7 357-4CH03-3AE0 (H)	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-
PtP Param for CP 340, CP 341, CP 440 and CP 441-1/2	V5.1.13 V5.1.12	HW: 6ES7 340-1*H0*-0AE0 HW: 6ES7 341-1*H0*-0AE0 HW: 6ES7 440-1CS00-0YE0 HW: 6ES7 441-*AA0*-0AE0	X	X	X	X	X	X	X	X	X	X	X	X	-	X
PtP Param for CP 340, CP 341, CP 440 and CP 441-1/2	V5.1.11	HW: 6ES7 340-1*H0*-0AE0 HW: 6ES7 341-1*H0*-0AE0 HW: 6ES7 440-1CS00-0YE0 HW: 6ES7 441-*AA0*-0AE0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
PtP Param for CP 340, CP 341, CP 440 and CP 441-1/2	V5.1.10 V5.1.9	HW: 6ES7 340-1*H0*-0AE0 HW: 6ES7 341-1*H0*-0AE0 HW: 6ES7 440-1CS00-0YE0 HW: 6ES7 441-*AA0*-0AE0	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-
Modbus Master	V3.1.7	6ES7 870-1AA00-0YA0 HW: 6ES7 341-1*H0*-0AE0 HW: 6ES7 441-2AA0*-0AE0	X	X	X	X	X	X	X	X	X	X	X	X	-	X
Modbus Master	V3.1.6	6ES7 870-1AA00-0YA0 HW: 6ES7 341-1*H0*-0AE0 HW: 6ES7 441-2AA0*-0AE0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
Modbus Master	V3.1.5 V3.1.4	6ES7 870-1AA00-0YA0 HW: 6ES7 341-1*H0*-0AE0 HW: 6ES7 441-2AA0*-0AE0	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-

Technological Functions			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
Modbus Slave	V3.1.8	6ES7 870-1AB00-0YA0 HW: 6ES7 341-1*H0*-0AE0 HW: 6ES7 441-2AA0*-0AE0	X	X	X	X	X	X	X	X	X	X	X	X	-	X
Modbus Slave	V3.1.7	6ES7 870-1AB00-0YA0 HW: 6ES7 341-1*H0*-0AE0 HW: 6ES7 441-2AA0*-0AE0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
Modbus Slave	V3.1.6 V3.1.5	6ES7 870-1AB00-0YA0 HW: 6ES7 341-1*H0*-0AE0 HW: 6ES7 441-2AA0*-0AE0	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-
Data Highway	V1.0.3	6ES7 870-1AE00-0YA0 HW: 6ES7 341-1*H0*-0AE0 HW: 6ES7 441-2AA0*-0AE0	X	X	X	X	X	X	X	X	X	X	X	X	-	X
Data Highway	V1.0.2	6ES7 870-1AE00-0YA0 HW: 6ES7 341-1*H0*-0AE0 HW: 6ES7 441-2AA0*-0AE0	X	X	X	X	-	-	-	-	-	-	-	-	-	-
CP 444	V1.2.2	6ES7 444-1MX00-7xG0 HW: 6ES7 444-1MX00-0XE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
CP 444	V1.2.1	6ES7 444-1MX00-7xG0 HW: 6ES7 444-1MX00-0XE0	-	-	-	-	-	-	-	-	-	-	-	-	-	-

Telecontrol			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
Telecontrol Server Basic	V3.1 Upd1		-	-	X	X	X	X	X	X	X	X	X	X	-	X
Telecontrol Server Basic	V3.0	6NH9 910-0AA21-0A*0	-	-	X	X	X	X	X	X	X	X	X	-	-	-
Telecontrol Server Basic	V2.0+SP3	6NH9 910-0AA20-0A*0	-	-	X	X	X	X	X	X	(-)	(-)	(-)	-	-	-

TeleService			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
TeleService Edition 08/2011	V6.1.5	6ES7 842-0CE00-0YE0	X	X	X	X	X	X	X	X	X	-	-	-	-	-
TeleService Edition 04/2011	V6.1.4	6ES7 842-0CE00-0YE0	X	X	X	(-)	-	-	-	-	-	-	-	-	-	-
TeleService Edition 11/2010	V6.1.3	6ES7 842-0CE00-0YE0	X	X	X	(-)	-	-	-	-	-	-	-	-	-	-
TeleService Edition 07/2008	V6.1.2	6ES7 842-0CE00-0YE0	X	X	-	-	-	-	-	-	-	-	-	-	-	-
TeleService Edition 11/2007 ¹⁾	V6.1.1	6ES7 842-0CE00-0YE0	(-)	X	-	-	-	-	-	-	-	-	-	-	-	-
TeleService Edition 01/2007 ¹⁾	V6.1	6ES7 842-0CE00-0YE0	(-)	(-)	-	-	-	-	-	-	-	-	-	-	-	-

¹⁾ Teleservice V6.1 and V6.1+SP1 cannot be used with STEP 7 V5.4+SP4 or higher, please use Teleservice V6.1+SP2 or higher

USB-Prommer			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
USB-Prommer	only HW ¹⁾	6ES7 792-0AA00-0XA0	X	X	X	X	X	X	X	X	X	X	X	X	(-)	X
USB-Prommer Edition 10/2007	V2.0	6ES7 792-0AA00-0XA0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
USB-Prommer	V1.1	6ES7 792-0AA00-0XA0	-	-	-	-	-	-	-	-	-	-	-	-	-	-

¹⁾ The functionality of USB Prommer is integrated in STEP 7 V5.5. For this reason, drivers no longer have to be installed in order to operate the USB-Prommer.

Version Cross Manager / Version Cross Checker			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
Version Cross Manager (VXM)	V9.0	6ES7 658-1CX58-2YA5	-	-	X	X	X	X	-	-	X	-	X	-	-	X
Version Cross Manager (VXM)	V8.2	6ES7 658-1CX28-2YA5	X	X	X	X	X	X	X	X	X	X	-	-	-	-
Version Cross Manager (VXM)	V7.1 SP3	6ES7 658-1CX17-2YA5	X	X	X	X	X	X	X	X	-	-	-	-	-	-
Version Cross Manager (VXM)	V7.1	6ES7 658-1CX17-2YA5	X	X	X ⁴⁾	(-)	-	-	-	-	-	-	-	-	-	-
Version Cross Manager (VXM)	V7.0	6ES7 658-1CX07-2YA5	X ³⁾	X ³⁾	-	-	-	-	-	-	-	-	-	-	-	-
Version Cross Checker (VXC) ²⁾	V6.1	6ES7 658-1CX16-2YB5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Version Cross Checker (VXC) ¹⁾	V6.0	6ES7 658-1CX06-2YA0	-	-	-	-	-	-	-	-	-	-	-	-	-	-

¹⁾ Minimum requirements: CFC V5.2+SP1 or higher

²⁾ Minimum requirements: CFC V6.1 or higher

³⁾ only as of Version Cross Manager V7.0+SP1 or higher

⁴⁾ only as of Version Cross Manager V7.1+SP2 or higher

Version Trail			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
Version Trail	V9.0	6ES7 658-1FX58-2YA5	-	-	X	X	X	X	-	-	X	-	X	-	-	X
Version Trail	V8.2	6ES7 658-1FX28-2YA5	X	X	X	X	X	X	X	X	X	X	-	-	-	-
Version Trail	V8.0	6ES7 658-1FX08-2YA5	X	X	X	X	X	X	X	X	-	-	-	-	-	-
Version Trail	V7.1	6ES7 658-1FX17-2YA5	X	X	X ¹⁾	(-)	-	-	-	-	-	-	-	-	-	-

¹⁾ only as of Version Trail V7.1+SP2 or higher

WinAC			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
WinAC MP ¹⁾	2008 (V4.1)	6ES7 671-*E*00-0YA0	X	-	-	-	-	-	-	-	-	-	-	-	-	-
WinAC ODK	V4.2	6ES7 806-1CC03-0BA0	X	-	-	-	-	X	-	-	X	-	-	-	-	-
WinAC RTX F	2010 SP3	6ES7 671-1RC08-0YA0	-	-	-	X	-	-	-	-	X	-	-	-	-	-
WinAC RTX F	2010 SP2	6ES7 671-1RC08-0YA0	X	-	X	X	-	-	-	-	X	-	-	-	-	-
WinAC RTX F	2010 SP1 (V4.6.1)	6ES7 671-1RC08-0YA0	X	-	X	X	-	-	-	-	X	-	-	-	-	-
WinAC RTX F	2010 (V4.6)	6ES7 671-1RC08-0YA0	X	-	X	X	-	-	-	-	X	-	-	-	-	-
WinAC RTX F	2009 (V4.5)	6ES7 671-1RC07-0YA0	X	-	-	-	-	-	-	-	-	-	-	-	-	-
WinAC RTX	2010 SP3	6ES7 671-0RC08-0YA0	-	-	-	X	-	-	-	-	X	-	-	-	-	-
WinAC RTX	2010 SP2	6ES7 671-0RC08-0YA0	X	-	X	X	-	-	-	-	X	-	-	-	-	-
WinAC RTX	2010 SP1 (V4.6.1)	6ES7 671-0RC08-0YA0	X	-	X	X	-	-	-	-	X	-	-	-	-	-
WinAC RTX	2010 (V4.6)	6ES7 671-0RC08-0YA0	X	-	X	X	-	-	-	-	X	-	-	-	-	-
WinAC RTX	2009 (V4.5)	6ES7 671-0RC07-0YA0	X	-	-	-	-	-	-	-	-	-	-	-	-	-
WinAC RTX	2008 (V4.4)	6ES7 671-0RC06-0YA0	X ²⁾	-	-	-	-	-	-	-	-	-	-	-	-	-
WinAC Slot 412 / 416	V4.0	6ES7 673-2CC40-0YA0 6ES7 673-6CC40-0YA0	X	-	-	-	-	-	-	-	-	-	-	-	-	-

¹⁾ additionally is STEP 7 V5.4+SP4 or higher and WinCC flexible 2008 or higher is also required

²⁾ only as of WinAC RTX 2008+SP1 or higher

WinCC			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
WinCC	V7.5	6AV6 381-2BP07-5AX0	-	-	-	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	(-)	X ⁴⁾
WinCC	V7.4 SP1	6AV6 381-2BP07-4AX0	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	-	X ⁴⁾
WinCC	V7.2	6AV6 381-2B*07-2AX0	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	-	-	-	-	-	-
WinCC	V7.0 SP3	6AV6 381-2B*07-0AX0	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	X ⁴⁾	-	-	-	-	-	-
WinCC	V7.0 SP2	6AV6 381-2B*07-0AX0	X ³⁾	X ³⁾	X ³⁾	-	-	-	-	-	-	-	-	-	-	-
WinCC	V7.0 SP1	6AV6 381-2B*07-0AX0	X ¹⁾	X ¹⁾	-	-	-	-	-	-	-	-	-	-	-	-
WinCC	V7.0	6AV6 381-2B*07-0AX0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WinCC	V6.2 SP3	6AV6 381-1B*06-2AX0	X	X	-	-	-	-	-	-	-	-	-	-	-	-
WinCC	V6.2 SP2	6AV6 381-1B*06-2AX0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WinCC	V6.2	6AV6 381-1B*06-2AX0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WinCC	V6.0+SP4	6AV6 381-1B*06-0EX0	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WinCC/ProAgent	V7.6	6AV6 371-1DG07-5AX0	-	-	-	X	X	X	-	-	X	-	-	-	-	X
WinCC/ProAgent	V7.3	6AV6 371-1DG07-3AX0	-	-	X	X	X	X	-	-	X	-	-	-	-	X
WinCC/ProAgent ²⁾	V7.0+SP2	6AV6 371-1DG07-0EX0	X	X	X	-	-	-	-	-	-	-	-	-	-	-
WinCC/ProAgent	V7.0+SP1	6AV6 371-1DG07-0EX0	X	X	(-)	-	-	-	-	-	-	-	-	-	-	-

Note: There are close dependencies between STEP 7, WinCC and WinCC/ProAgent and between various service packs. The latest information on released combinations is available on the Internet at: <http://support.automation.siemens.com/WW/view/en/21928032>

For joint operation of STEP 7 V5.4 SP4 with WinCC 7.0 and V7.0 SP1 under Windows Vista you will need to install the SIMATIC NET CD 2007 available on the WinCC data carrier.

¹⁾ not tested with STEP 7 V5.5+SP1 or higher

²⁾ WinCC/ProAgent V7.0+SP2 only in conjunction with WinCC V7.0+SP2+Update 1 or higher

³⁾ STEP 7 V5.4+SP1 only with WinCC V7.0+SP2 Upd4 or higher, not tested with STEP 7 V5.5+SP2 or higher

⁴⁾ only as of STEP 7 V5.5+SP2

WinCC flexible			STEP 7 V5.5								STEP 7 V5.6					
Product Name	Version	Order Number	Win XP SP3	Win 2003 SP2	Win 7	Win 7 SP1	Win 7 (64)	Win 7 SP1 (64)	Win 2008 R2 (64)	Win 2008 R2 SP1 (64)	Win 7 SP1 (64)	Win 2008 R2 SP1 (64)	Win 2012 R2 (64)	Win 2016 (64)	Win 2019 (64)	Win 10 (64)
WinCC flexible (Micro/Compact/Standard/Advanced)	2008 SP5	6AV6 613-0AA51-3CA5	-	-	-	X	-	X	-	-	X	-	-	-	-	X
WinCC flexible Runtime	2008 SP5	6AV6 613-1BA51-3CA0	-	-	X	X	X	X	-	-	X	-	-	-	-	X
WinCC flexible (Micro/Compact/Standard/Advanced)	2008 SP3 (V1.4)	6AV6 61*-0AA01-3AA5	X	-	X ²⁾	X ²⁾	X ²⁾	X ²⁾	-	-	X ²⁾	X ²⁾	-	-	-	-
WinCC flexible Runtime	2008 SP3 (V1.4)	6AV6 613-1*A01-3AA0	X	-	X ²⁾	X ²⁾	X ²⁾	X ²⁾	-	-	X ²⁾	X ²⁾	-	-	-	-
WinCC flexible (Micro/Compact/Standard/Advanced)	2008	6AV6 61*-0AA01-3AA5	X ¹⁾	-	X ¹⁾	-	-	-	-	-	-	-	-	-	-	-
WinCC flexible Runtime	2008	6AV6 613-1*A01-3AA0	X ¹⁾	-	X ¹⁾	-	-	-	-	-	-	-	-	-	-	-

Note: Further information on compatibility with WinCC flexible can be found on the Internet at: <http://support.automation.siemens.com/WWW/view/de/22635649>

¹⁾ only as of WinCC flexible 2008+SP2

²⁾ only as of STEP 7 V5.5 + SP2 or higher