

Product discontinuation as of October 1, 2021

MLFB	Product
6AV6381-2BT07-2AH0	WinCC RC 102400, V7.2 SD
6AV6371-2BM17-2AJ0	WinCC Powerpack RC 2048/8192 V7.2 SD
6AV6371-2BG17-2AJ0	WinCC Powerpack RC 512/2048 V7.2 SD
6AV6381-2BN07-2AH0	WinCC RC 512, V7.2 SD
6AV6371-2BQ17-2AJ0	WinCC Powerp RC 102400/153600 V7.2 SD
6AV6381-2BM07-2AH0	WinCC RC 128, V7.2 SD
6AV6371-2BD17-2AJ0	WinCC Powerpack RC 128/512 V7.2 SD
6AV6381-2BS07-2AH0	WinCC RC 8192, V7.2 SD
6AV6371-2BR17-2AJ0	WinCC Powerp RC 153600/262144 V7.2 SD
6AV6381-2BP07-2AH0	WinCC RC 2048, V7.2 SD
6AV6381-2BQ07-2AH0	WinCC RC 65536, V7.2 SD
6AV6381-2BU07-2AH0	WinCC RC 153600, V7.2 SD
6AV6381-2BV07-2AH0	WinCC RC 262144, V7.2 SD
6AV6371-2BN17-2AJ0	WinCC Powerpack RC 8192/65536 V7.2 SD
6AV6371-2BP17-2AJ0	WinCC Powerp RC 65536/102400 V7.2 SD
6AV6371-2BG17-2AX0	WinCC / Powerpack RC 512/2048 V7.2
6AV6371-2BD17-2AX0	WinCC / Powerpack RC 128/512 V7.2
6AV6381-2BS07-2AX0	WinCC RC 8192, V7.2
6AV6381-2BU07-2AV0	WinCC RC 153600, V7.2 Asia
6AV6381-2BP07-2AV0	WinCC RC 2048, V7.2 Asia
6AV6381-2BT07-2AX0	WinCC RC 102400, V7.2
6AV6381-2BV07-2AV0	WinCC RC 262144, V7.2 Asia
6AV6381-2BV07-2AX0	WinCC RC 262144, V7.2
6AV6381-2BU07-2AX0	WinCC RC 153600, V7.2
6AV6381-2BQ07-2AV0	WinCC RC 65536, V7.2 Asia
6AV6381-2BP07-2AX0	WinCC RC 2048, V7.2
6AV6381-2BQ07-2AX0	WinCC RC 65536, V7.2
6AV6381-2BS07-2AV0	WinCC RC 8192, V7.2 Asia
6AV6381-2BT07-2AV0	WinCC RC 102400, V7.2 Asia
6AV6371-2BM17-2AX0	WinCC / Powerpack RC 2048/8192 V7.2
6AV6381-2BN07-2AX0	WinCC RC 512, V7.2
6AV6381-2BN07-2AV0	WinCC RC 512, V7.2 Asia
6AV6381-2BM07-2AX0	WinCC RC 128, V7.2
6AV6381-2BM07-2AV0	WinCC RC 128, V7.2 Asia
6AV6371-2BR17-2AX0	WinCC / Powerpack RC 153600/262144 V7.2
6AV6371-2BQ17-2AX0	WinCC / Powerpack RC 102400/153600 V7.2
6AV6371-2BP17-2AX0	WinCC / Powerpack RC 65536/102400 V7.2
6AV6371-2BN17-2AX0	WinCC / Powerpack RC 8192/65536 V7.2
6AV6381-2DM07-2AX0	WinCC RC 500000, V7.2
6AV6381-2CB07-2AH0	WinCC RC Client V7.2 SD
6AV6381-2CB07-2AX0	WinCC RC Client V7.2
6AV6381-2CB07-2AV0	WinCC RC Client V7.2 Asia
6AV6371-2BR07-2AJ0	WinCC Powerp RT 153600/262144 V7.2 SD
6AV6371-2BQ07-2AJ0	WinCC Powerp RT 102400/153600 V7.2 SD
6AV6381-2BC07-2AH0	WinCC RT 128, V7.2 SD
6AV6371-2BN07-2AJ0	WinCC Powerpack RT 8192/65536 V7.2 SD

MLFB	Product
6AV6381-2BD07-2AH0	WinCC RT 512, V7.2 SD
6AV6371-2BD07-2AJ0	WinCC Powerpack RT 128/512 V7.2 SD
6AV6371-2BG07-2AJ0	WinCC Powerpack RT 512/2048 V7.2 SD
6AV6371-2BP07-2AJ0	WinCC Powerp RT 65536/102400 V7.2 SD
6AV6371-2BM07-2AJ0	WinCC Powerpack RT 2048/8192 V7.2 SD
6AV6381-2BK07-2AH0	WinCC RT 153600, V7.2 SD
6AV6381-2BL07-2AH0	WinCC RT 262144, V7.2 SD
6AV6381-2BE07-2AH0	WinCC RT 2048, V7.2 SD
6AV6381-2BJ07-2AH0	WinCC RT 102400, V7.2 SD
6AV6381-2BH07-2AH0	WinCC RT 8192, V7.2 SD
6AV6381-2BF07-2AH0	WinCC RT 65536, V7.2 SD
6AV6371-2BP07-2AX0	WinCC / Powerpack RT 65536/102400 V7.2
6AV6371-2BM07-2AX0	WinCC / Powerpack RT 2048/8192 V7.2
6AV6371-2BG07-2AX0	WinCC / Powerpack RT 512/2048 V7.2
6AV6371-2BD07-2AX0	WinCC / Powerpack RT 128/512 V7.2
6AV6381-2BF07-2AX0	WinCC RT 65536, V7.2
6AV6381-2BF07-2AV0	WinCC RT 65536, V7.2 Asia
6AV6381-2BE07-2AX0	WinCC RT 2048, V7.2
6AV6381-2BE07-2AV0	WinCC RT 2048, V7.2 Asia
6AV6381-2BD07-2AV0	WinCC RT 512, V7.2 Asia
6AV6381-2BH07-2AX0	WinCC RT 8192, V7.2
6AV6381-2BC07-2AX0	WinCC RT 128, V7.2
6AV6381-2BC07-2AV0	WinCC RT 128, V7.2 Asia
6AV6381-2BD07-2AX0	WinCC RT 512, V7.2
6AV6381-2BL07-2AV0	WinCC RT 262144, V7.2 Asia
6AV6381-2BH07-2AV0	WinCC RT 8192, V7.2 Asia
6AV6381-2BK07-2AX0	WinCC RT 153600, V7.2
6AV6381-2BK07-2AV0	WinCC RT 153600, V7.2 Asia
6AV6381-2BJ07-2AX0	WinCC RT 102400, V7.2
6AV6381-2BJ07-2AV0	WinCC RT 102400, V7.2 Asia
6AV6381-2BL07-2AX0	WinCC RT 262144, V7.2
6AV6371-2BR07-2AX0	WinCC / Powerpack RT 153600/262144 V7.2
6AV6371-2BQ07-2AX0	WinCC / Powerpack RT 102400/153600 V7.2
6AV6371-2BN07-2AX0	WinCC / Powerpack RT 8192/65536 V7.2
6AV6381-2DC07-2AX0	WinCC RT 500000, V7.2
6AV6381-2CA07-2AH0	WinCC RT Client V7.2 SD
6AV6381-2CA07-2AX0	WinCC RT Client V7.2
6AV6381-2CA07-2AV0	WinCC RT Client V7.2 Asia
6AV6381-1XX07-2AP0	WinCC V7.2 EPL-Master
6AV6371-1HV17-2AX0	WinCC/Audit RC V7.2 DL
6AV6371-1DV17-2AX0	WinCC/Audit RC V7.2
6AV6371-1HV07-2AX0	WinCC/Audit RT, V7.2 DL
6AV6371-1DV07-2AX0	WinCC/ Audit RT, V7.2
6AV6372-1DC07-2AX0	WinCC/Calendar Scheduler V7.2
6AV6371-1HV27-2AX0	WinCC/Changecontrol V7.2 DL
6AV6371-1DV27-2AX0	WinCC/Changecontrol V7.2
6AV6377-1DR07-2AF3	FL Migrationspaket Connectivity Pack
6AV6371-1HR07-2AX0	WinCC/Connectivity Pack V7.2 SD
6AV6371-1HR17-2AX0	WinCC/Connectivity Station V7.2 SD

MLFB	Product
6AV6371-1DR17-2AX0	WinCC/Connectivity Station V7.2
6AV6371-1DR07-2AX0	WinCC/Connectivity Pack V7.2
6AV6371-1HN07-2CX0	WinCC/Datamonitor V7.2, 25 Clients SD
6AV6371-1HN07-2AX0	WinCC/Datamonitor V7.2, 3 Clients SD
6AV6371-1HN07-2BX0	WinCC/Datamonitor V7.2, 10 Clients SD
6AV6371-1JN07-2CD0	WinCC/Datamonitor V7.2, Powerp 25/50 SD
6AV6371-1HN07-2DX0	WinCC/Datamonitor V7.2, 50 Clients SD
6AV6371-1JN07-2LA0	WinCC/Datamonitor V7.2, Powerpack 1/3 SD
6AV6371-1JN07-2BC0	WinCC/Datamonitor V7.2, Powerp 10/25 SD
6AV6371-1JN07-2AB0	WinCC/Datamonitor V7.2, Powerp 3/10 SD
6AV6371-1HN07-2LX0	WinCC/Datamonitor V7.2, 1 Client SD
6AV6371-1DN07-2LA0	WinCC Datamonitor V7.2, Powerpack 1/3
6AV6371-1DN07-2AB0	WinCC Datamonitor V7.2, Powerpack 3/10
6AV6371-1DN07-2AX0	WinCC Datamonitor V7.2, 3 Clients
6AV6371-1DN07-2BC0	WinCC Datamonitor V7.2, Powerpack 10/25
6AV6371-1DN07-2BX0	WinCC Datamonitor V7.2, 10 Clients
6AV6371-1DN07-2CD0	WinCC Datamonitor V7.2, Powerpack 25/50
6AV6371-1DN07-2CX0	WinCC Datamonitor V7.2, 25 Clients
6AV6371-1DN07-2DX0	WinCC Datamonitor V7.2, 50 Clients
6AV6371-1DN07-2LX0	WinCC Datamonitor V7.2, 1 Client
6AV6372-1DD07-2AX0	WinCC/Event Notifier V7.2
6AV6371-1HX07-2BX0	WinCC/IND.Databridge V7.2, 512 SD
6AV6371-1JX07-2AB0	WinCC/IND.Databridge V7.2, 128 -> 512 SD
6AV6371-1HX07-2CX0	WinCC/IND.Databridge V7.2, 2048 SD
6AV6371-1HX07-2AX0	WinCC/IND.Databridge V7.2, 128 SD
6AV6371-1JX07-2CD0	WinCC/IND.Databrdg V7.2, 2048 ->10000 SD
6AV6371-1JX07-2BC0	WinCC/IND.Databridg V7.2, 512 -> 2048 SD
6AV6371-1HX07-2DX0	WinCC/IND.Databridge V7.2, 10000 SD
6AV6371-1DX07-2CD0	WinCC/IND.Databridge V7.2, 2048 ->10000
6AV6371-1DX07-2CX0	WinCC OPT. IND.Databridge V7.2, 2048
6AV6371-1DX07-2AB0	WinCC/IND.Databridge V7.2, 128 -> 512
6AV6371-1DX07-2AX0	WinCC OPT. IND.Databridge V7.2, 128
6AV6371-1DX07-2BX0	WinCC OPT. IND.Databridge V7.2, 512
6AV6371-1DX07-2DX0	WinCC OPT. IND.Databridge V7.2, 10000
6AV6371-1DX07-2BC0	WinCC/IND.Databridge V7.2, 512 -> 2048
6AV6371-1GC07-2AX0	WinCC/ODK V7.2 SD
6AV6371-1CC07-2AX0	SIMATIC WinCC/ODK V7.2
6AV6372-2HG07-2AA0	WinCC/Performance Mon.V7.2, Basic P. SD
6AV6372-2DG07-2AA0	WinCC/Performance Mon. V7.2, Basic P.
6AV6371-1HG07-2AX0	WinCC/ProAgent V7.2 DL
6AV6371-1DG07-2AX0	WinCC /ProAgent V7.2
6AV6371-1HF07-2AX0	WinCC/Redundancy V7.2 LK SD
6AV6371-1CF07-2AX0	WinCC/Redundancy V7.2
6AV6371-1HA07-2AX0	WinCC/Server V7.2 LK SD
6AV6371-1CA07-2AX0	WinCC/Server V7.2
6AV6371-1HB07-2AX0	WinCC/User Archives V7.2 LK SD
6AV6371-1CB07-2AX0	WinCC/User Archives V7.2
6AV6371-1JH07-2MB0	WinCC/Web Navigator V7.2,Powerp 5/10 SD
6AV6371-1HH07-2MX0	WinCC/Web Navigator V7.2, 5 Clients SD

MLFB	Product
6AV6371-1HH07-2AM0	WinCC/Web Navigator V7.2,Powerp 3/5 SD
6AV6371-1JH07-2LA0	WinCC/Web Navigator V7.2,Powerp 1/3 SD
6AV6371-1HH07-2EX0	WinCC/Web Navigator V7.2, Diag.Client SD
6AV6371-1JH07-2CD0	WinCC/Web Navigator V7.2,Powerp 25/50 SD
6AV6371-1JH07-2BC0	WinCC/Web Navigator V7.2,Powerp 10/25 SD
6AV6371-1HH07-2HX0	WinCC/Web Navigator V7.2, 150 Clients SD
6AV6371-1HH07-2DX0	WinCC/Web Navigator V7.2, 50 Clients SD
6AV6371-1HH07-2AX0	WinCC/Web Navigator V7.2, 3 Clients SD
6AV6371-1HH07-2BX0	WinCC/Web Navigator V7.2, 10 Clients SD
6AV6371-1HH07-2CX0	WinCC/Web Navigator V7.2, 25 Clients SD
6AV6371-1HH07-2GX0	WinCC/Web Navigator V7.2, 100 Clients SD
6AV6371-1JH07-2AM0	WinCC/Web Navigator V7.2,Powerp 3/5 SD
6AV6371-1HH07-2LX0	WinCC/Web Navigator V7.2, 1 Client SD
6AV6371-1DH07-2EX0	WinCC Web Navigator V7.2, Diag.Client
6AV6371-1DH07-2DX0	WinCC/Web Navigator V7.2, 50 Clients
6AV6371-1DH07-2CX0	WinCC/Web Navigator V7.2, 25 Clients
6AV6371-1DH07-2CD0	WinCC Web Navigator V7.2,Powerpack 25/50
6AV6371-1DH07-2BX0	WinCC/Web Navigator V7.2, 10 Clients
6AV6371-1DH07-2BC0	WinCC Web Navigator V7.2,Powerpack 10/25
6AV6371-1DH07-2AM0	WinCC Web Navigator V7.2,Powerpack 3/5
6AV6371-1DH07-2LA0	WinCC Web Navigator V7.2,Powerpack 1/3
6AV6371-1DH07-2AX0	WinCC/Web Navigator V7.2, 3 Clients
6AV6371-1DH07-2HX0	WinCC/Web Navigator V7.2, 150 Clients
6AV6371-1DH07-2MX0	WinCC/Web Navigator V7.2, 5 Clients
6AV6371-1DH07-2GX0	WinCC/Web Navigator V7.2, 100 Clients
6AV6371-1DH07-2LX0	WinCC/Web Navigator V7.2, 1 Client
6AV6371-1HH07-2JX0	WinCC/Web Load Balancing, V7.2 SD
6AV6371-1HH07-2FJ0	WinCC/Web Load Balancing Step up V7.2 SD
6AV6371-1DH07-2FJ0	WinCC Web Load Balancing Step up V7.2
6AV6371-1DH07-2JX0	WinCC Web Load Balancing, V7.2
6AV6371-1DH07-2MB0	WinCC Web Navigator V7.2,Powerpack 5/10
6AV6371-1HH07-2FX0	WinCC/Web Navigator V7.2, Diag.Server SD
6AV6371-1DH07-2FX0	WinCC Web Navigator V7.2, Diag.Server
6AV6371-1JQ17-2GJ0	WinCC/Archiv Powerp V7.2, 80000/120000 SD
6AV6371-1HQ17-2GX0	WinCC/Archiv V7.2, 80000 Archive Tags SD
6AV6371-1HQ17-2EX0	WinCC/Archiv V7.2, 30000 Archive Tags SD
6AV6371-1JQ17-2AB0	WinCC/Archive Powerp V7.2, 1500/5000 SD
6AV6371-1JQ17-2BC0	WinCC/Archive Powerp V7.2, 5000/10000 SD
6AV6371-1JQ17-2CE0	WinCC/Archiv Powerp V7.2, 10000/30000 SD
6AV6371-1JQ17-2EG0	WinCC/Archiv Powerp V7.2, 30000/80000 SD
6AV6371-1HQ17-2CX0	WinCC/Archiv V7.2, 10000 Archive Tags SD
6AV6371-1HQ17-2AX0	WinCC/Archive V7.2, 1500 Archive Tags SD
6AV6371-1HQ17-2BX0	WinCC/Archiv V7.2, 5000 Archive Tags SD
6AV6371-1HQ17-2JX0	WinCC/Archiv V7.2, 120000 Archive Tags SD
6AV6371-1DQ17-2AB0	WinCC Archiv Powerp. V7.2, 1500/5000
6AV6371-1DQ17-2AX0	WinCC/Archive V7.2, 1500 Archive Tags
6AV6371-1DQ17-2BC0	WinCC Archiv Powerp. V7.2, 5000/10000
6AV6371-1DQ17-2BX0	WinCC/Archive V7.2, 5000 Archive Tags
6AV6371-1DQ17-2CE0	WinCC Archiv Powerp. V7.2, 10000/30000

MLFB	Product
6AV6371-1DQ17-2CX0	WinCC/Archive V7.2, 10000 Archive Tags
6AV6371-1DQ17-2EG0	WinCC Archiv Powerp. V7.2, 30000/80000
6AV6371-1DQ17-2EX0	WinCC/Archive V7.2, 30000 Archive Tags
6AV6371-1DQ17-2GJ0	WinCC Archiv Powerp. V7.2, 80000/120000
6AV6371-1DQ17-2JX0	WinCC/Archive V7.2, 120000 Archive Tags
6AV6371-1DQ17-2GX0	WinCC/Archive V7.2, 80000 Archive Tags