

SIMATIC Panel PC 670 - stocked variants

6AV7721-1AC10-0AA0	10" TFT display Celeron 1,2 GHz, 128 MB RAM 20 Gbyte harddisk + CD-ROM 230V power supply Europe without operating system
6AV7721-1AC10-0AB0	10" TFT display Celeron 1,2 GHz, 128 MB RAM 20 Gbyte harddisk + CD-ROM 230V power supply Europe Windows NT 4.0 German
6AV7721-1AC10-0AC0	10" TFT display Celeron 1,2 GHz, 128 MB RAM 20 Gbyte harddisk + CD-ROM 230V power supply Europe Windows NT 4.0 English

6AV7723-1BC10-0AA0	12" TFT display Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe without operating system
6AV7723-1BC10-0AB0	12" TFT display Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe Windows NT 4.0 German
6AV7723-1BC10-0AC0	12" TFT display Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe Windows NT 4.0 English
6AV7723-1BC10-0AD0	12" TFT display Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe Windows 2000 multi language

6AV7722-1BC10-0AA0	12" TFT display, touch Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe without operating system
6AV7722-1BC10-0AB0	12" TFT display, touch Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe Windows NT 4.0 German

6AV7722-1BC10-0AC0	12" TFT display, touch Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe Windows NT 4.0 English
6AV7722-1BC10-0AD0	12" TFT display, touch Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe Windows 2000 multi language

6AV7725-1BC10-0AA0	15" TFT display Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe without operating system
6AV7725-1BC10-0AB0	15" TFT display Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe Windows NT 4.0 German
6AV7725-1BC10-0AC0	15" TFT display Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe Windows NT 4.0 English
6AV7725-1BC10-0AD0	15" TFT display Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe Windows 2000 multi language

6AV7724-1BC10-0AA0	15" TFT display, touch Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe without operating system
6AV7724-1BC10-0AB0	15" TFT display, touch Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe Windows NT 4.0 German
6AV7724-1BC10-0AC0	15" TFT display, touch Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe Windows NT 4.0 English
6AV7724-1BC10-0AD0	15" TFT display, touch Pentium III 1,26 GHz, 128 MB RAM 20 Gbyte hard disk + CD-ROM 230V power supply Europe Windows 2000 multi language