

Product discontinuation as of April 1, 2023

MLFB	Product
6AV9681-1JH07-3GH0	WinCC Web Navigtr V7.3,Powerp 100/150 DL
6AV9681-1DH07-3DG0	WinCC Web Navigator V7.3,Powerp 50/100
6AV9681-1DH07-3GH0	WinCC Web Navigator V7.3,Powerp 100/150
6AV9681-1JH07-3DG0	WinCC Web Navigtr V7.3,Powerp 50/100 DL
6AV6371-1CF07-3AX0	WinCC/Redundancy V7.3
6AV6371-1CB07-3AX0	WinCC/User Archives V7.3
6AV6371-1DG07-3AX0	WinCC /ProAgent V7.3
6AV6371-1CA07-3AX0	WinCC/Server V7.3
6AV6371-1CC07-3AX0	SIMATIC WinCC/ODK V7.3
6AV6371-1DN07-3AB0	WinCC Datamonitor V7.3, Powerpack 3/10
6AV6371-1DN07-3AX0	WinCC Datamonitor V7.3, 3 Clients
6AV6371-1DN07-3BC0	WinCC Datamonitor V7.3, Powerpack 10/25
6AV6371-1DN07-3BX0	WinCC Datamonitor V7.3, 10 Clients
6AV6371-1DN07-3CD0	WinCC Datamonitor V7.3, Powerpack 25/50
6AV6371-1DH07-3AM0	WinCC Web Navigator V7.3,Powerpack 3/5
6AV6371-1DH07-3AX0	WinCC/Web Navigator V7.3, 3 Clients
6AV6371-1DH07-3BC0	WinCC Web Navigator V7.3,Powerpack 10/25
6AV6371-1DH07-3BX0	WinCC/Web Navigator V7.3, 10 Clients
6AV6371-1DH07-3CD0	WinCC Web Navigator V7.3,Powerpack 25/50
6AV6371-1DH07-3CX0	WinCC/Web Navigator V7.3, 25 Clients
6AV6371-1DH07-3DX0	WinCC/Web Navigator V7.3, 50 Clients
6AV6371-1DH07-3EX0	WinCC Web Navigator V7.3, Diag.Client
6AV6371-1DH07-3FX0	WinCC Web Navigator V7.3, Diag.Server
6AV6371-1DH07-3GX0	WinCC/Web Navigator V7.3, 100 Clients
6AV6371-1DH07-3HX0	WinCC/Web Navigator V7.3, 150 Clients
6AV6371-1DH07-3JX0	WinCC Web Load Balancing, V7.3
6AV6371-1DH07-3LA0	WinCC Web Navigator V7.3,Powerpack 1/3
6AV6371-1DH07-3LX0	WinCC/Web Navigator V7.3, 1 Client
6AV6371-1DH07-3MB0	WinCC Web Navigator V7.3,Powerpack 5/10
6AV6371-1DH07-3MX0	WinCC/Web Navigator V7.3, 5 Clients
6AV6371-1DN07-3CX0	WinCC Datamonitor V7.3, 25 Clients
6AV6371-1DN07-3DX0	WinCC Datamonitor V7.3, 50 Clients
6AV6371-1DN07-3LA0	WinCC Datamonitor V7.3, Powerpack 1/3
6AV6371-1DN07-3LX0	WinCC Datamonitor V7.3, 1 Client
6AV6371-1DQ17-3EX0	WinCC/Archive V7.3, 30000 Archive Tags
6AV6371-1DQ17-3GX0	WinCC/Archive V7.3, 80000 Archive Tags
6AV6371-1DQ17-3AB0	WinCC Archiv Powerp. V7.3, 1500/5000
6AV6371-1DQ17-3AX0	WinCC/Archive V7.3, 1500 Archive Tags
6AV6371-1DQ17-3BC0	WinCC Archiv Powerp. V7.3, 5000/10000
6AV6371-1DQ17-3BX0	WinCC/Archive V7.3, 5000 Archive Tags

MLFB	Product
6AV6371-1DQ17-3CE0	WinCC Archiv Powerp. V7.3, 10000/30000
6AV6371-1DQ17-3CX0	WinCC/Archive V7.3, 10000 Archive Tags
6AV6371-1DQ17-3EG0	WinCC Archiv Powerp. V7.3, 30000/80000
6AV6371-1DR07-3AX0	WinCC/Connectivity Pack V7.3
6AV6371-1DR17-3AX0	WinCC/Connectivity Station V7.3
6AV6371-1DV17-3AX0	WinCC/Audit RC V7.3
6AV6371-1DV07-3AX0	WinCC/ Audit RT, V7.3
6AV6371-1HA07-3AX0	WinCC/Server V7.3 LK DL
6AV6371-1GC07-3AX0	WinCC/ODK V7.3 DL
6AV6371-1DX07-3AB0	WinCC/IND.Databridge V7.3, 128 -> 512
6AV6371-1DX07-3AX0	WinCC OPT. IND.Databridge V7.3, 128
6AV6371-1DX07-3BC0	WinCC/IND.Databridge V7.3, 512 -> 2048
6AV6371-1DX07-3BX0	WinCC OPT. IND.Databridge V7.3, 512
6AV6371-1DX07-3CD0	WinCC/IND.Databridge V7.3, 2048 -> 10000
6AV6371-1DX07-3CX0	WinCC OPT. IND.Databridge V7.3, 2048
6AV6371-1DX07-3DX0	WinCC OPT. IND.Databridge V7.3, 10000
6AV6371-1DV27-3AX0	WinCC/Changecontrol V7.3
6AV6371-1HF07-3AX0	WinCC/Redundancy V7.3 LK DL
6AV6371-1HH07-3FX0	WinCC/Web Navigator V7.3, Diag.Server DL
6AV6371-1HH07-3GX0	WinCC/Web Navigator V7.3, 100 Clients DL
6AV6371-1HB07-3AX0	WinCC/User Archives V7.3 LK DL
6AV6371-1HN07-3AX0	WinCC/Datamonitor V7.3, 3 Clients DL
6AV6371-1HG07-3AX0	WinCC/ProAgent V7.3 DL
6AV6371-1HN07-3BX0	WinCC/Datamonitor V7.3, 10 Clients DL
6AV6371-1HH07-3AX0	WinCC/Web Navigator V7.3, 3 Clients DL
6AV6371-1HH07-3BX0	WinCC/Web Navigator V7.3, 10 Clients DL
6AV6371-1HH07-3CX0	WinCC/Web Navigator V7.3, 25 Clients DL
6AV6371-1HN07-3LX0	WinCC/Datamonitor V7.3, 1 Client DL
6AV6371-1HQ17-3GX0	WinCC/Archiv V7.3, 80000 Archive Tags DL
6AV6371-1HH07-3DX0	WinCC/Web Navigator V7.3, 50 Clients DL
6AV6371-1HH07-3LX0	WinCC/Web Navigator V7.3, 1 Client DL
6AV6371-1HH07-3MX0	WinCC/Web Navigator V7.3, 5 Clients DL
6AV6371-1HN07-3CX0	WinCC/Datamonitor V7.3, 25 Clients DL
6AV6371-1JX07-3AB0	WinCC/IND.Databridge V7.3, 128 -> 512 DL
6AV6371-1JX07-3BC0	WinCC/IND.Databridg V7.3, 512 -> 2048 DL
6AV6371-1HV07-3AX0	WinCC/Audit RT, V7.3 DL
6AV6371-1HH07-3EX0	WinCC/Web Navigator V7.3, Diag.Client DL
6AV6371-1HR17-3AX0	WinCC/Connectivity Station V7.3 DL
6AV6371-1HN07-3DX0	WinCC/Datamonitor V7.3, 50 Clients DL
6AV6371-1HQ17-3EX0	WinCC/Archiv V7.3, 30000 Archive Tags DL
6AV6371-2BG07-3AJ0	WinCC Powerpack RT 512/2048 V7.3 DL
6AV6371-2BG07-3AX0	WinCC / Powerpack RT 512/2048 V7.3
6AV6371-1JX07-3CD0	WinCC/IND.Databrdg V7.3, 2048 -> 10000 DL

MLFB	Product
6AV6371-2BD07-3AX0	WinCC / Powerpack RT 128/512 V7.3
6AV6371-1HR07-3AX0	WinCC/Connectivity Pack V7.3 DL
6AV6371-1HQ17-3CX0	WinCC/Archiv V7.3, 10000 Archive Tags DL
6AV6371-1HV27-3AX0	WinCC/Changecontrol V7.3 DL
6AV6371-1HH07-3HX0	WinCC/Web Navigator V7.3, 150 Clients DL
6AV6371-1HQ17-3AX0	WinCC/Archive V7.3, 1500 Archive Tags DL
6AV6371-1HQ17-3BX0	WinCC/Archiv V7.3, 5000 Archive Tags DL
6AV6371-1HH07-3JX0	WinCC/Web Load Balancing, V7.3 DL
6AV6371-2BN17-3AJ0	WinCC Powerpack RC 8192/65536 V7.3 DL
6AV6371-2BN17-3AX0	WinCC / Powerpack RC 8192/65536 V7.3
6AV6371-1HV17-3AX0	WinCC/Audit RC V7.3 DL
6AV6371-2BD17-3AX0	WinCC / Powerpack RC 128/512 V7.3
6AV6371-2BD07-3AJ0	WinCC Powerpack RT 128/512 V7.3 DL
6AV6371-1JQ17-3EG0	WinCC/Archiv Powerp V7.3, 30000/80000 DL
6AV6371-2BM07-3AJ0	WinCC Powerpack RT 2048/8192 V7.3 DL
6AV6371-1JQ17-3AB0	WinCC/Archive Powerp V7.3, 1500/5000 DL
6AV6371-1JQ17-3BC0	WinCC/Archive Powerp V7.3, 5000/10000 DL
6AV6371-2BM07-3AX0	WinCC / Powerpack RT 2048/8192 V7.3
6AV6371-1JN07-3AB0	WinCC/Datamonitor V7.3, Powerp 3/10 DL
6AV6371-1JN07-3BC0	WinCC/Datamonitor V7.3, Powerp 10/25 DL
6AV6371-2BM17-3AJ0	WinCC Powerpack RC 2048/8192 V7.3 DL
6AV6371-1JH07-3BC0	WinCC/Web Navigator V7.3,Powerp 10/25 DL
6AV6371-1JH07-3CD0	WinCC/Web Navigator V7.3,Powerp 25/50 DL
6AV6371-1JH07-3LA0	WinCC/Web Navigator V7.3,Powerp 1/3 DL
6AV6371-1JH07-3MB0	WinCC/Web Navigator V7.3,Powerp 5/10 DL
6AV6371-1JQ17-3CE0	WinCC/Archiv Powerp V7.3, 10000/30000 DL
6AV6371-1HX07-3AX0	WinCC/IND.Databridge V7.3, 128 DL
6AV6371-1HX07-3BX0	WinCC/IND.Databridge V7.3, 512 DL
6AV6371-1HX07-3CX0	WinCC/IND.Databridge V7.3, 2048 DL
6AV6371-1JH07-3AM0	WinCC/Web Navigator V7.3,Powerp 3/5 DL
6AV6371-1HX07-3DX0	WinCC/IND.Databridge V7.3, 10000 DL
6AV6371-2BP17-3AJ0	WinCC Powerp RC 65536/102400 V7.3 DL
6AV6371-2BP07-3AJ0	WinCC Powerp RT 65536/102400 V7.3 DL
6AV6371-1JN07-3CD0	WinCC/Datamonitor V7.3, Powerp 25/50 DL
6AV6371-1JN07-3LA0	WinCC/Datamonitor V7.3, Powerpack 1/3 DL
6AV6372-1DD07-3AX0	WinCC/Event Notifier V7.3
6AV6371-2BP07-3AX0	WinCC / Powerpack RT 65536/102400 V7.3
6AV6371-2BR07-3AX0	WinCC / Powerpack RT 153600/262144 V7.3
6AV6371-2BN07-3AJ0	WinCC Powerpack RT 8192/65536 V7.3 DL
6AV6371-2BQ07-3AX0	WinCC / Powerpack RT 102400/153600 V7.3
6AV6371-2BD17-3AJ0	WinCC Powerpack RC 128/512 V7.3 DL
6AV6371-2BP17-3AX0	WinCC / Powerpack RC 65536/102400 V7.3
6AV6371-2BN07-3AX0	WinCC / Powerpack RT 8192/65536 V7.3

MLFB	Product
6AV6371-2BQ07-3AJ0	WinCC Powerp RT 102400/153600 V7.3 DL
6AV6372-1HC07-3AX0	WinCC/Calendar Scheduler V7.3 DL
6AV6371-2BG17-3AJ0	WinCC Powerpack RC 512/2048 V7.3 DL
6AV6371-2BG17-3AX0	WinCC / Powerpack RC 512/2048 V7.3
6AV6371-2BM17-3AX0	WinCC / Powerpack RC 2048/8192 V7.3
6AV6371-2BR17-3AJ0	WinCC Powerp RC 153600/262144 V7.3 DL
6AV6371-2BR17-3AX0	WinCC / Powerpack RC 153600/262144 V7.3
6AV6372-1HD07-3AX0	WinCC/Event Notifier V7.3 DL
6AV6372-2BJ07-3BA0	WinCC/SES V7.3, Extension 5 Units
6AV6371-2BQ17-3AJ0	WinCC Powerp RC 102400/153600 V7.3 DL
6AV6371-2BQ17-3AX0	WinCC / Powerpack RC 102400/153600 V7.3
6AV6371-2BR07-3AJ0	WinCC Powerp RT 153600/262144 V7.3 DL
6AV6372-1DC07-3AX0	WinCC/Calendar Scheduler V7.3
6AV6372-2DJ07-3AA0	WinCC/SES V7.3, Basic Pckg.
6AV6381-2BD07-3AV0	WinCC RT 512, V7.3 Asia
6AV6381-2BD07-3AX0	WinCC RT 512, V7.3
6AV6381-2BE07-3AH0	WinCC RT 2048, V7.3 DL
6AV6381-2BE07-3AV0	WinCC RT 2048, V7.3 Asia
6AV6381-2BE07-3AX0	WinCC RT 2048, V7.3
6AV6381-2BC07-3AV0	WinCC RT 128, V7.3 Asia
6AV6381-2BC07-3AX0	WinCC RT 128, V7.3
6AV6381-2BD07-3AH0	WinCC RT 512, V7.3 DL
6AV6381-2BC07-3AH0	WinCC RT 128, V7.3 DL
6AV6381-2BH07-3AH0	WinCC RT 8192, V7.3 DL
6AV6381-2BH07-3AV0	WinCC RT 8192, V7.3 Asia
6AV6381-2BH07-3AX0	WinCC RT 8192, V7.3
6AV6381-2BF07-3AX0	WinCC RT 65536, V7.3
6AV6381-2BF07-3AV0	WinCC RT 65536, V7.3 Asia
6AV6381-2BF07-3AH0	WinCC RT 65536, V7.3 DL
6AV6381-2BL07-3AH0	WinCC RT 262144, V7.3 DL
6AV6381-2BJ07-3AX0	WinCC RT 102400, V7.3
6AV6381-2BK07-3AH0	WinCC RT 153600, V7.3 DL
6AV6381-2BK07-3AV0	WinCC RT 153600, V7.3 Asia
6AV6381-2BK07-3AX0	WinCC RT 153600, V7.3
6AV6381-2BM07-3AV0	WinCC RC 128, V7.3 Asia
6AV6381-2BP07-3AV0	WinCC RC 2048, V7.3 Asia
6AV6381-2BP07-3AX0	WinCC RC 2048, V7.3
6AV6381-2BN07-3AH0	WinCC RC 512, V7.3 DL
6AV6381-2BN07-3AV0	WinCC RC 512, V7.3 Asia
6AV6381-2BN07-3AX0	WinCC RC 512, V7.3
6AV6381-2BM07-3AX0	WinCC RC 128, V7.3
6AV6381-2BJ07-3AH0	WinCC RT 102400, V7.3 DL
6AV6381-2BJ07-3AV0	WinCC RT 102400, V7.3 Asia

MLFB	Product
6AV6381-2BM07-3AH0	WinCC RC 128, V7.3 DL
6AV6381-2BP07-3AH0	WinCC RC 2048, V7.3 DL
6AV6381-2BL07-3AV0	WinCC RT 262144, V7.3 Asia
6AV6381-2BL07-3AX0	WinCC RT 262144, V7.3
6AV6381-2BQ07-3AV0	WinCC RC 65536, V7.3 Asia
6AV6381-2BQ07-3AX0	WinCC RC 65536, V7.3
6AV6381-2BU07-3AV0	WinCC RC 153600, V7.3 Asia
6AV6381-2BU07-3AX0	WinCC RC 153600, V7.3
6AV6381-2BT07-3AH0	WinCC RC 102400, V7.3 DL
6AV6381-2BT07-3AV0	WinCC RC 102400, V7.3 Asia
6AV6381-2BS07-3AH0	WinCC RC 8192, V7.3 DL
6AV6381-2BU07-3AH0	WinCC RC 153600, V7.3 DL
6AV6381-2BQ07-3AH0	WinCC RC 65536, V7.3 DL
6AV6381-2BS07-3AV0	WinCC RC 8192, V7.3 Asia
6AV6381-2BS07-3AX0	WinCC RC 8192, V7.3
6AV6381-2BV07-3AV0	WinCC RC 262144, V7.3 Asia
6AV6381-2BT07-3AX0	WinCC RC 102400, V7.3
6AV6381-2BV07-3AX0	WinCC RC 262144, V7.3
6AV6381-2CA07-3AH0	WinCC RT Client V7.3 DL
6AV6381-2BV07-3AH0	WinCC RC 262144, V7.3 DL
6AV6381-2CB07-3AX0	WinCC RC Client V7.3
6AV6381-2CB07-3AV0	WinCC RC Client V7.3 Asia
6AV6381-2DC07-3AX0	WinCC RT 500000, V7.3
6AV6381-2DM07-3AX0	WinCC RC 500000, V7.3
6AV6381-2CA07-3AV0	WinCC RT Client V7.3 Asia
6AV6381-2CA07-3AX0	WinCC RT Client V7.3
6AV6381-2CB07-3AH0	WinCC RC Client V7.3 DL