

function modules of the S7-300		interface module of the ET200M station	place behind IM 153-1 6ES7 153-1AA03-0XB0		place behind IM 153-2 6ES7 153-2BA02-0XB0		place behind IM 153-2 FO 6ES7 153-2BB00-0XB0	
module name		order number of the FM	configured with					
			STEP 7*	GSD**	STEP 7*	GSD**	STEP 7*	GSD**
function modules for S7-300								
	SM338 POS INPUT 3xSSI	6ES7338-4BC01-0AB0	x	x	x	x	x	x
	counter module FM 350-1 (1-channel)	6ES7350-1AH03-0AE0	x	-	x	-	x	-
	counter module FM 350-2 (8-channel)	6ES7350-2AH01-0AE0	x	-	x	-	x	-
	FM 351 rapid/creep	6ES7351-1AH01-0AE0	x	-	x	-	x	-
	FM 351 rapid/creep	6ES7351-1AH02-0AE0	x	-	x	-	x	-
	FM 352 electronic cam controller	6ES7352-1AH02-0AE0	x	-	x	-	x	-
	FM 352-5 high speed boolean processor	6ES7352-5AH00-0AE0	x***	x	x***	x	x***	x
	FM 352-5 high speed boolean processor	6ES7352-5AH01-0AE0	x***	x	x***	x	x***	x
	FM 352-5 high speed boolean processor	6ES7352-5AH10-0AE0	x***	x	x***	x	x***	x
	FM 352-5 high speed boolean processor	6ES7352-5AH11-0AE0	x***	x	x***	x	x***	x
	FM 353 for positioning with stepper motor	6ES7353-1AH01-0AE0	-	-	x	-	x	-
	FM 354 for positioning with servo motor	6ES7354-1AH01-0AE0	-	-	x	-	x	-
closed-loop control module								
	FM 355 C control module continuous	6ES7355-0VH10-0AE0	-	-	x	-	x	-
	FM 355 S control module step/pulse	6ES7355-1VH10-0AE0	-	-	x	-	x	-
	FM 355-2 C temperature control module continuous	6ES7355-2CH00-0AE0	x	-	x	-	x	-
	FM 355-2 S temperature control module step/pulse	6ES7355-2SH00-0AE0	x	-	x	-	x	-

x --> configurable

- --> not configurable

* --> configurable within STEP 7 (hardware-catalog under PROFIBUS DP > ET200M > IM 153-1 / IM153-2)

** --> configurable with GSD-File

(configurable after Installation of GSD-File from hardware-catalog under PROFIBUS DP > Additional Field Devices > I/O > ET200M)

*** --> only configurable with appropriate add-on to STEP7