

MLFB list

MLFB
3RK4320-3AQ54-0BA2
3RK4320-3AQ54-0BA3
3RK4320-3AQ54-1BA2
3RK4320-3AQ54-1BA3
3RK4320-3BQ54-0BA2
3RK4320-3BQ54-0BA3
3RK4320-3BQ54-1BA2
3RK4320-3BQ54-1BA3
3RK4320-3CQ54-0BA2
3RK4320-3CQ54-0BA3
3RK4320-3CQ54-1BA2
3RK4320-3CQ54-1BA3
3RK4320-3DQ54-0BA2
3RK4320-3DQ54-0BA3
3RK4320-3DQ54-1BA2
3RK4320-3DQ54-1BA3
3RK4320-3EQ54-0BA2
3RK4320-3EQ54-0BA3
3RK4320-3EQ54-1BA2
3RK4320-3EQ54-1BA3
3RK4320-3FQ54-0BA2
3RK4320-3FQ54-0BA3
3RK4320-3FQ54-1BA2
3RK4320-3FQ54-1BA3
3RK4320-3GQ54-0BA2
3RK4320-3GQ54-0BA3
3RK4320-3GQ54-1BA2
3RK4320-3GQ54-1BA3
3RK4320-3HQ54-0BA2
3RK4320-3HQ54-0BA3
3RK4320-3HQ54-1BA2
3RK4320-3HQ54-1BA3
3RK4320-3JQ54-0BA2
3RK4320-3JQ54-0BA3
3RK4320-3JQ54-1BA2
3RK4320-3JQ54-1BA3
3RK4320-3KQ54-0BA2
3RK4320-3KQ54-0BA3
3RK4320-3KQ54-1BA2
3RK4320-3KQ54-1BA3
3RK4320-3LQ54-0BA2
3RK4320-3LQ54-0BA3
3RK4320-3LQ54-1BA2
3RK4320-3LQ54-1BA3
3RK4320-3MQ54-0BA2
3RK4320-3MQ54-0BA3
3RK4320-3MQ54-1BA2
3RK4320-3MQ54-1BA3
3RK4320-3NQ54-0BA2
3RK4320-3NQ54-0BA3
3RK4320-3NQ54-1BA2
3RK4320-3NQ54-1BA3
3RK4320-3PQ54-0BA2
3RK4320-3PQ54-0BA3
3RK4320-3PQ54-1BA2
3RK4320-3PQ54-1BA3
3RK4320-5DQ64-0BA2

MLFB list

MLFB
3RK4320-5DQ64-0BA3
3RK4320-5DQ64-1BA2
3RK4320-5DQ64-1BA3
3RK4320-5JQ64-0BA2
3RK4320-5JQ64-0BA3
3RK4320-5JQ64-1BA2
3RK4320-5JQ64-1BA3
3RK4320-5PQ64-0BA2
3RK4320-5PQ64-0BA3
3RK4320-5PQ64-1BA2
3RK4320-5PQ64-1BA3
8PV5051-1BA10
8PV5051-1BA11
8PV5051-1BA20
8PV5051-1BA21

code conversion table

MLFB alt	MLFB M200D AS-I Basic	Notice	MLFB M200D AS-I Standard	Notice
3RK4320-3AQ54-0BA2	3RK1315-6KS41-2AA3	1), 2)	3RK1325-6KS41-2AA3	1), 2), 3)
3RK4320-3AQ54-0BA3	3RK1315-6KS41-2AA3	1), 2)	3RK1325-6KS41-2AA3	1), 2), 3)
3RK4320-3BQ54-0BA2	3RK1315-6KS41-2AA3	1), 2)	3RK1325-6KS41-2AA3	1), 2), 3)
3RK4320-3BQ54-0BA3	3RK1315-6KS41-2AA3	1), 2)	3RK1325-6KS41-2AA3	1), 2), 3)
3RK4320-3CQ54-0BA2	3RK1315-6KS41-2AA3	1), 2)	3RK1325-6KS41-2AA3	1), 2), 3)
3RK4320-3CQ54-0BA3	3RK1315-6KS41-2AA3	1), 2)	3RK1325-6KS41-2AA3	1), 2), 3)
3RK4320-3DQ54-0BA2	3RK1315-6KS41-2AA3	1), 2)	3RK1325-6KS41-2AA3	1), 2), 3)
3RK4320-3DQ54-0BA3	3RK1315-6KS41-2AA3	1), 2)	3RK1325-6KS41-2AA3	1), 2), 3)
3RK4320-3EQ54-0BA2	3RK1315-6KS41-2AA3	1), 2)	3RK1325-6KS41-2AA3	1), 2), 3)
3RK4320-3EQ54-0BA3	3RK1315-6KS41-2AA3	1), 2)	3RK1325-6KS41-2AA3	1), 2), 3)
3RK4320-3FQ54-0BA2	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3FQ54-0BA3	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3GQ54-0BA2	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3GQ54-0BA3	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3HQ54-0BA2	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3HQ54-0BA3	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3JQ54-0BA2	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3JQ54-0BA3	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3KQ54-0BA2	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3KQ54-0BA3	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3LQ54-0BA2	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3LQ54-0BA3	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3MQ54-0BA2	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3MQ54-0BA3	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3NQ54-0BA2	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3NQ54-0BA3	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3PQ54-0BA2	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-3PQ54-0BA3	3RK1315-6LS41-2AA3	1), 2)	3RK1325-6LS41-2AA3	1), 2), 3)
3RK4320-5DQ64-0BA2	3RK1315-6KS71-2AA3	1), 2)	3RK1325-6KS71-2AA3	1), 2), 3)
3RK4320-5DQ64-0BA3	3RK1315-6KS71-2AA3	1), 2)	3RK1325-6KS71-2AA3	1), 2), 3)
3RK4320-5JQ64-0BA2	3RK1315-6NS71-2AA3	1), 2)	3RK1325-6LS71-2AA3	1), 2), 3)
3RK4320-5JQ64-0BA3	3RK1315-6NS71-2AA3	1), 2)	3RK1325-6LS71-2AA3	1), 2), 3)
3RK4320-5PQ64-0BA2	-	M200D only up to 9A	-	M200D only up to 9A
3RK4320-5PQ64-0BA3	-	M200D only up to 9A	-	M200D only up to 9A
3RK4320-3AQ54-1BA2	3RK1315-6KS41-3AA3	1), 2)	3RK1325-6KS41-3AA3	1), 2), 3)
3RK4320-3AQ54-1BA3	3RK1315-6KS41-3AA3	1), 2)	3RK1325-6KS41-3AA3	1), 2), 3)
3RK4320-3BQ54-1BA2	3RK1315-6KS41-3AA3	1), 2)	3RK1325-6KS41-3AA3	1), 2), 3)

code conversion table

MLFB alt	MLFB M200D AS-I Basic	Notice	MLFB M200D AS-I Standard	Notice
3RK4320-3BQ54-1BA3	3RK1315-6KS41-3AA3	1), 2)	3RK1325-6KS41-3AA3	1), 2), 3)
3RK4320-3CQ54-1BA2	3RK1315-6KS41-3AA3	1), 2)	3RK1325-6KS41-3AA3	1), 2), 3)
3RK4320-3CQ54-1BA3	3RK1315-6KS41-3AA3	1), 2)	3RK1325-6KS41-3AA3	1), 2), 3)
3RK4320-3DQ54-1BA2	3RK1315-6KS41-3AA3	1), 2)	3RK1325-6KS41-3AA3	1), 2), 3)
3RK4320-3DQ54-1BA3	3RK1315-6KS41-3AA3	1), 2)	3RK1325-6KS41-3AA3	1), 2), 3)
3RK4320-3EQ54-1BA2	3RK1315-6KS41-3AA3	1), 2)	3RK1325-6KS41-3AA3	1), 2), 3)
3RK4320-3EQ54-1BA3	3RK1315-6KS41-3AA3	1), 2)	3RK1325-6KS41-3AA3	1), 2), 3)
3RK4320-3FQ54-1BA2	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3FQ54-1BA3	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3GQ54-1BA2	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3GQ54-1BA3	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3HQ54-1BA2	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3HQ54-1BA3	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3JQ54-1BA2	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3JQ54-1BA3	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3KQ54-1BA2	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3KQ54-1BA3	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3LQ54-1BA2	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3LQ54-1BA3	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3MQ54-1BA2	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3MQ54-1BA3	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3NQ54-1BA2	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3NQ54-1BA3	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3PQ54-1BA2	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-3PQ54-1BA3	3RK1315-6LS41-3AA3	1), 2)	3RK1325-6LS41-3AA3	1), 2), 3)
3RK4320-5DQ64-1BA2	3RK1315-6KS71-3AA3	1), 2)	3RK1325-6KS71-3AA3	1), 2), 3)
3RK4320-5DQ64-1BA3	3RK1315-6KS71-3AA3	1), 2)	3RK1325-6KS71-3AA3	1), 2), 3)
3RK4320-5JQ64-1BA2	3RK1315-6NS71-3AA3	1), 2)	3RK1325-6LS71-3AA3	1), 2), 3)
3RK4320-5JQ64-1BA3	3RK1315-6NS71-3AA3	1), 2)	3RK1325-6LS71-3AA3	1), 2), 3)
3RK4320-5PQ64-1BA2	-	M200D only up to 9A	-	M200D only up to 9A
3RK4320-5PQ64-1BA3	-	M200D only up to 9A	-	M200D only up to 9A

Notice

- | | |
|----|--|
| 1) | Power supply with HAN Q4/2 plug on M200D |
| 2) | Motor cable with HAN Q8/0 plug on M200D |
| 3) | It be two AS-i slave addresses needed |