

## DESCRIPTION

## PRODUCT COVERED:

Magnetic Motor Controller, Type 3TF68, followed by 22, 33 or 44, followed by OC, 1D or 1Q.

## GENERAL:

This device is an open type, 3 pole vacuum contactor intended to connect motor directly across the line.

Rating

<u>Voltage ac</u>	<u>Maximum Horse Power 3 ph - 3 poles breaking</u>	<u>Full Load Amperes</u>
200	231	630
230-240	266	630
460-480	530	630
<u>575-600</u>	664	630

Supplementary Current Rating: 630 A, 630 FLA, 3780 LRA, 600 V ac, 3 ph, 3 poles general purpose.

Auxiliary Switch - Heavy pilot duty A600, P600.

Operating Coils: 110 through 600 V ac, including 115, 120, 230, 240, 460, 480, and 575 V ac. 24 through 250 V dc, including 60, 110, 125, 220 and 230 V dc.