

Measured Components of Komm-IE V3.0 (ID15)

Components		Type	MLFB	Version
Sending station	S7-300	CPU 315-2DP	6ES7 315-2AG10-0AB0	V2.0
		CPU 315-2 PN/DP	6ES7 315-2EH13-0AB0	V2.6
		CPU 317-2PN/DP	6ES7 317-2EK13-0AB0	V2.6
		CPU 319-3 PN/DP	6ES7 318-3EL00-0AB0	V2.6
		CP 343-1 EX30	6GK7 343-1EX30-0XE0	V2.0
	S7-400	CPU 414-2 DP	6ES7 414-2XK05-0AB0	V5.1
		CPU 414-3 PN/DP	6ES7 414-205-0AB0	V5.1
		CPU 416-3PN/DP	6ES7 416-3ER05-0AB0	V5.1
		CP 443-1 (Adv)	6GK7 443-1E41-0XE0	V1.0
	PCbased	WinAC RTX 2005	6ES7 671-1RC05-0YA0	on BoxPC 627
WinAC RTX 2008		6ES7 671-1RC06-0YA0	on BoxPC 627B	
Net	switch	SCALANCE X108	6GK5 108-0BA00-2AA3	
	Security	SCALANCE S612	6GK5 612-0BA00-2AA3	V2.1
Receiving station	S7-300	CPU 315-2 PN/DP	6ES7 315-2EH13-0AB0	V2.6
		CP 343-1 EX30	6GK7 343-1EX30-0XE0	V2.0
	S7-400	CPU 414-3PN/DP	6ES7 414-3EM05-0AB0	V5.1
		CP 443.1 EX20	6GK7 443-1EX20-0XE0	V1.0
		CP 443-1 Adv	6GK7 443-1EX41-0XE0	V1.0
STEP 7 Professional		6ES7 810-5CC08-0YA6	V5.4 SP3	
SIMATIC iMap STEP 7 Add On			V 3.0.4	