

Measured Components of Komm-IE V1.0 (ID6)

Components		Type	MLFB	Version
Sending station	S7-300	CPU 315-2DP	6ES7 315-2AG10-0AB0	V 2.0
		CPU 315-2 PN/DP	6ES7 315-2EG10-0AB0	V 2.3
		CPU 317-2 DP	6ES7 317-2AJ10-0AB0	V 2.1
		CPU 317-2PN/DP	6ES7 317-2EJ10-0AB0	V 2.3
		CP 343-1 lean	6GK7 343-1CX00-0XE0	V 1.1
		CP 343-1	6GK7 343-1EX21-0XE0	V 1.0
	S7-400	CPU 414-2 DP	6ES7 414-2XG04-0AB0	V 4.0
		CPU 416-2 DP	6ES7 416-2XK04-0AB0	V 4.0
		CP 443-1	6GK7 443-1EX11-0XE0	V 2.5
		CP 443-1 Adv	6GK7 443-1EX40-0XE0	V 2.1
Net	switch	SCALANCE X108	6GK5 108-0BA00-2AA3	
Receiving station	S7-300	CPU 315-2 PN/DP	6ES7 315-2EG10-0AB0	V2.3
	S7-400	CPU 414-2DP	6ES7 414-2XG04-0AB0	
		CP 443.1 Adv.	6GK7 443-1EX40-0XE0	V2.1
STEP 7 Professional		V 5.3 SP2	6ES7 810-5CC08-0YA6	V5.3 SP2