

## Measured Components of Komm-IE V2.0 (ID9)

Components		Type	MLFB	Version
Sending station	S7-300	CPU 315-2DP	6ES7 315-2AG10-0AB0	V 2.0
		CPU 315-2 PN/DP	6ES7 315-2EG10-0AB0	V 2.3
		CPU 317-2 DP	6ES7 317-2AJ10-0AB0	V 2.1
		CPU 317-2PN/DP	6ES7 317-2EJ13-0AB0	V 2.3
		CPU 319-3 PN/DP	6ES7 318-3EL00-0AB0	V 2.4
		CP 343-1 lean	6GK7 343-1CX00-0XE0	V 1.1
		CP 343-1	6GK7 343-1EX21-0XE0	V 1.1
		CP 343-1 IT	6GK7 343-1GX21-0XE0	V 1.0
	S7-400	CPU 414-2 DP	6ES7 414-2XG04-0AB0	V 4.0
		CPU 414-3 PN/DP	6ES7 414-3EM05-0AB0	V 5.0
		CPU 416-2 DP	6ES7 416-2XK04-0AB0	V 4.0
		CPU 416-3 PN/DP	6ES7 416-3ER05-0AB0	V 5.0
		CPU 416-3PN	6ES7 416-3ER05-0AB0	V 5.3
		CP 443-1	6GK7 443-1EX11-0XE0	V 2.6
		CP 443-1 Adv	6GK7 443-1EX40-0XE0	V2.4
CP 443-1 Adv	6GK7 443-1EX41-0XE0	V1.0		
PCbased	WinAC RTX 2005	6ES7 671-0RC05-0YA0	V4.2	
Net	switch	SCALANCE X108	6GK5 108-0BA00-2AA3	
	Security	SCALANCE S613	6GK5 613-0BA00-1AA3	V2.3
Receiving station	S7-300	CPU 315-2 PN/DP	6ES7 315-2EG10-0AB0	V2.3
		CP 343-1 EX30	6GK7 343-1EX30-0XE0	V2.1
		CP 343-1 Adv GX30	6GK7 343-1GX30-0XE0	V1.0
	S7-400	CPU 414-3PN/DP	6ES7 414-2XG04-0AB0	V4.0
		CP 443.1 Adv.	6GK7 443-1EX40-0XE0	V2.4
STEP 7 Professional		V 5.4	6ES7 810-5CC08-0YA6	V5.4