

Configurations for SIMATIC Flat Panel Monitor

6AV7 8 6 1 - [] [] [] [] 0 - [] A A 0 SIMATIC Flat Panel Monitor

[1] *)
[2] *)
[4] [1]
[3] *)

[A]
[T]

[X]
[B]

[0]
[1] [1]

Display Size
12"
15"
17"
19"

Operating mode:
Display Device without Operating Possibility
Touchscreen (analog resistive)

Power Supplies:
24 Volt DC; not with extended Version
100-230 Volt AC (inkl. Euro Cable)/24 Volt DC

Special functions
standard: up 5m distance
extended: up 30m distance+Special functions:
-ship certifications/approvals
-dimmbable
-ATEX Zone 22 (in preparation)

*) 0: für Standardvarianten 1: für extended Varianten

Accessories:

6AV7 6 7 1 - 2 B A 0 0 - 0 A A 0	Touch protection slide for 12" Front Panel
6AV7 6 7 1 - 4 B A 0 0 - 0 A A 0	Touch protection slide for 15" Front Panel
6AV7 6 7 2 - 1 C F 0 0 - 0 A A 0	Touch protection slide for 17" Front Panel
6AV7 6 7 2 - 1 C E 0 0 - 0 A A 0	Touch protection slide for 19" Front Panel
6AV7 6 7 2 - 8 K E 0 0 - 0 A A 0	19 inch rack fixing elements for 17"/ 19"

Accessories: for standard types up to 5m (6AV861-...0.-1...)

6AV7 8 6 0 - 0 A H 3 0 - 0 A A 0	VGA-cable industrial grade 3m	6AV7860-0AH30-0AA0
6AV7 8 6 0 - 0 A H 5 0 - 0 A A 0	VGA-cable industrial grade 5m	6AV7860-0AH50-0AA0
6AV7 8 6 0 - 0 B H 3 0 - 0 A A 0	DVI-D-cable industrial grade 3m	6AV7860-0BH30-0AA0
6AV7 8 6 0 - 0 B H 5 0 - 0 A A 0	DVI-D-cable industrial grade 5m	6AV7860-0BH50-0AA0
6AV7 8 6 0 - 0 C H 3 0 - 0 A A 0	USB-cable industrial grade 3m	6AV7860-0CH30-0AA0
6AV7 8 6 0 - 0 C H 5 0 - 0 A A 0	USB-cable industrial grade 5m	6AV7860-0CH50-0AA0

Accessories: for extendend types up to 30m, with special functions (6AV7861-...1.-1...)

6AV7 8 6 0 - 1 E X 2 1 - 0 A A 1	Set of cables 10m (USB/Cat5, USB-Transceiver;DVI)	6AV7860-1EX21-0AA1
6AV7 8 6 0 - 1 E X 2 1 - 5 A A 1	Set of cables 15m (USB/Cat5, USB-Transceiver;DVI)	6AV7860-1EX21-5AA1
6AV7 8 6 0 - 1 E X 2 2 - 0 A A 1	Set of cables 20m (USB/Cat5, USB-Transceiver;DVI)	6AV7860-1EX22-0AA1
6AV7 8 6 0 - 1 E X 2 3 - 0 A A 1	Set of cables 30m (USB/Cat5, USB-Transceiver;DVI)	6AV7860-1EX23-0AA1