WinCC V7.0 + SP 1 (03/2009) **released for Windows VISTA Ultimate, Business and Enterprise SP 1, Windows XP Professional SP2/3, Windows 2003 Server R2 SP2, Windows 2003 Server SP2**		**WinCC communication chanel**			
		SIMATIC S7 Protocol Suite		**SIMATIC S5**	
		ISO_L4	TCP/IP	ISO_L4	TCP/IP
SIMATIC NET --- CD: Edition 2008 (10/2008) products					
CP 1612 (The software SOFTNET-S7 must be order seperatly)	6GK1161-2AA00	X	X		X[1]
SOFTNET-S7 2008 released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1704-1CW71-3AA0	X	X		
Upgrade for SOFTNET-S7 2006/2007 (V6.4, V7.0) released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1704-1CW00-3AE0	X	X		
Upgrade for SOFTNET-S7 V6.0, V6.1, V6.2 and 2005 (V6.3) released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1704-1CW00-3AE1	X	X		
SOFTNET-S7 Lean 2008 released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1704-1LW71-3AA0	X[2]	X[2]		
Upgrade for SOFTNET-S7 Lean 2006/2007 (V6.4, V7.0) released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1704-1LW00-3AE0	X[2]	X[2]		
Upgrade for SOFTNET-S7 Lean V6.0, V6.1, V6.2 and 2005 (V6.3) released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1704-1LW00-3AE1	X[2]	X[2]		
CP 1613 A2 PCI-Card (32 Bit) for connection from PG/PC to Industrial Ethernet (communication software S7-1613 must be order seperatly)	6GK1161-3AA01	X	X	X	X[1]
CP 1623 PCI-Express Card (32 Bit) for connection from PG/PC to Industrial Ethernet (communication software S7-1613 must be order seperatly)	6GK1162-3AA00	X	X	X	X[1]
S7-1613 2008 released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1716-1CB71-3AA0	X	X	X	X
Upgrade for S7-1613 2006/2007 (V6.4, V7.0) released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1716-1CB00-3AE0	X	X	X	X
Upgrade for S7-1613 V6.0, V6.1, V6.2 und 2005 (V6.3) released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1716-1CB00-3AE1	X	X	X	X

x **=** SIMATIC NET products are tested and released with WinCC = please see the operating system restriction from WinCC / NET

1) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily
2) SOFTNET-S7 Lean 2006 are included in the Package WinCC V6.2 +SP2

WinCC V7.0 (05/2008) **released for Windows VISTA Ultimate, Business and Enterprise, Windows XP Professional SP2, Windows 2003 Server R2 SP2, Windows 2003 Server SP2**		**WinCC communication chanel**			
		SIMATIC S7 Protocol Suite		**SIMATIC S5**	
		ISO_L4	TCP/IP	ISO_L4	TCP/IP
SIMATIC NET --- CD: Edition 2007 +HF1 (02/2008) products					
CP 1612 (The software SOFTNET-S7 must be order seperatly)	6GK1161-2AA00	X	X		X1
SOFTNET-S7 2007 released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1704-1CW70-3AA0	X	X		
Upgrade for SOFTNET-S7 2006 (V6.4) released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1704-1CW00-3AE0	X	X		
Upgrade for SOFTNET-S7 V6.0, V6.1, V6.2 and 2005 (V6.3) released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1704-1CW00-3AE1	X	X		
SOFTNET-S7 Lean 2007 released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1704-1LW70-3AA0	X2	X2		
Upgrade for SOFTNET-S7 Lean 2006 (V6.4)	6GK1704-1LW00-3AE0	X2	X2		
Upgrade for SOFTNET-S7 Lean V6.0, V6.1, V6.2 and 2005 (V6.3) released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1704-1LW00-3AE1	X2	X2		
CP 1613 A2 PCI-Card (32 Bit) for connection from PG/PC to Industrial Ethernet (communication software S7-1613 must be order seperatly)	6GK1161-3AA01	X	X	X	X1
CP 1623 PCI-Express Card (32 Bit) for connection from PG/PC to Industrial Ethernet (communication software S7-1613 must be order seperatly)	6GK1162-3AA00	X	X	X	X1
S7-1613 2007 released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1716-1CB70-3AA0	X	X	X	X
Upgrade for S7-1613 2006 (V6.4) released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1716-1CB00-3AE0	X	X	X	X
Upgrade for S7-1613 V6.0, V6.1, V6.2 und 2005 (V6.3) released for Windows Vista Ultimate/Business, Windows XP Profesional and Windows 2003 Server	6GK1716-1CB00-3AE1	X	X	X	X

x = SIMATIC NET products are tested and released with WinCC

= please see the operating system restriction from WinCC / NET

1) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily
2) SOFTNET-S7 Lean 2006 are included in the Package WinCC V6.2 +SP2

WinCC V6.2 + SP3 (05/2009) **6AV6381-1B*06-0EX0** **released for Windows 2000 Professional SP4, Windows XP Professional SP2/3, Windows 2003 Server R2 SP2,Windows 2003 Server SP2**		**WinCC communication chanel**			
		SIMATIC S7 Protocol Suite		**SIMATIC S5**	
		ISO_L4	TCP/IP	ISO_L4	TCP/IP
SIMATIC NET --- CD: Edition 2006 (01/2007) Products					
CP 1612 (The software SOFTNET-S7 must be order seperatly)	6GK1161-2AA00	**X**	**X**		**X**[1]
SOFTNET-S7 2006 released for Windows 2000 (Profesional/Server), Windows XP Professional and Windows 2003 Server	6GK1704-1CW64-3AA0	**X**[2]	**X**[2]		
Upgrade for SOFTNET S7 V6.0, V6.1, V6.2 und 2005 (V6.3) released for Windows 2000 (Profesional/Server), Windows XP Profesional and Windows 2003 Server	6GK1704-1CW00-3AE0	**X**[2]	**X**[2]		
SOFTNET-S7 Lean 2006 released for Windows 2000 (Profesional/Server), Windows XP Professional and Windows 2003 Server	6GK1704-1LW64-3AA0	**X**[2]	**X**[2]		
Upgrade for SOFTNET-S7 Lean V6.0, V6.1, V6.2 and 2005 (V6.3) released for Windows 2000 (Profesional/Server), Windows XP Profesional and Windows 2003 Server	6GK1704-1LW00-3AE0	**X**[2]	**X**[2]		
CP 1613 PCI-Card for connection from PG/PC to Industrial Ethernet (communication software Kommunikationssoftware S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA00	**X**	**X**	**X**	**X**[1]
CP 1613 A2 PCI-Card (32 Bit) for connection from PG/PC to Industrial Ethernet (communication software Kommunikationssoftware S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA01	**X**	**X**	**X**	**X**[1]
S7-1613 2006 released for Windows 2000 (Profesional/Server), Windows XP Profesional and Windows 2003 Server	6GK1716-1CB64-3AA0	**X**	**X**	**X**	**X**
Upgrade for S7-1613 V6.0, V6.1, V6.2 und 2005 (V6.3) released for Windows 2000 (Profesional/Server), Windows XP Profesional and Windows 2003 Server	6GK1716-1CB00-3AE0	**X**	**X**	**X**	**X**
TF-1613 2006 released for Windows 2000 (Profesional/Server) and Windows XP Profesional	6GK1716-1TB64-3AA0			**X**	
Upgrade for TF-1613 V6.0, V6.1, V6.2 and 2005 (V6.3) Released for Windows 2000 (Profesional/Server) and Windows XP Profesional	6GK1716-1TB00-3AE0			**X**	

x **=** SIMATIC NET products are tested and released with WinCC = please see the operating system restriction from WinCC / NET

1) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily

2) SOFTNET-S7 Lean 2006 are included in the Package WinCC V6.2 +SP2

WinCC V6.2 + SP2 (01/2008) **6AV6381-1B*06-0EX0** **released for Windows 2000 Professional SP4, Windows XP Professional SP2, Windows 2003 Server R2 SP2,Windows 2003 Server SP2**		**WinCC communication chanel**			
		SIMATIC S7 Protocol Suite		**SIMATIC S5**	
		ISO_L4	TCP/IP	ISO_L4	TCP/IP
SIMATIC NET --- CD: Edition 2006 (01/2007) Products					
CP 1612 (The software SOFTNET-S7 must be order seperatly)	6GK1161-2AA00	X	X		X_1
SOFTNET-S7 2006 released for Windows 2000 (Profesional/Server), Windows XP Professional and Windows 2003 Server	6GK1704-1CW64-3AA0	X_2	X_2		
Upgrade for SOFTNET S7 V6.0, V6.1, V6.2 und 2005 (V6.3) released for Windows 2000 (Profesional/Server), Windows XP Profesional and Windows 2003 Server	6GK1704-1CW00-3AE0	X_2	X_2		
SOFTNET-S7 Lean 2006 released for Windows 2000 (Profesional/Server), Windows XP Professional and Windows 2003 Server	6GK1704-1LW64-3AA0	X_2	X_2		
Upgrade for SOFTNET-S7 Lean V6.0, V6.1, V6.2 and 2005 (V6.3) released for Windows 2000 (Profesional/Server), Windows XP Profesional and Windows 2003 Server	6GK1704-1LW00-3AE0	X_2	X_2		
CP 1613 PCI-Card for connection from PG/PC to Industrial Ethernet (communication software Kommunikationssoftware S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA00	X	X	X	X_1
CP 1613 A2 PCI-Card (32 Bit) for connection from PG/PC to Industrial Ethernet (communication software Kommunikationssoftware S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA01	X	X	X	X_1
S7-1613 2006 released for Windows 2000 (Profesional/Server), Windows XP Profesional and Windows 2003 Server	6GK1716-1CB64-3AA0	X	X	X	X
Upgrade for S7-1613 V6.0, V6.1, V6.2 und 2005 (V6.3) released for Windows 2000 (Profesional/Server), Windows XP Profesional and Windows 2003 Server	6GK1716-1CB00-3AE0	X	X	X	X
TF-1613 2006 released for Windows 2000 (Profesional/Server) and Windows XP Profesional	6GK1716-1TB64-3AA0			X	
Upgrade for TF-1613 V6.0, V6.1, V6.2 and 2005 (V6.3) Released for Windows 2000 (Profesional/Server) and Windows XP Profesional	6GK1716-1TB00-3AE0			X	

x = SIMATIC NET products are tested and released with WinCC

= please see the operating system restriction from WinCC / NET

1) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily

2) SOFTNET-S7 Lean 2006 are included in the Package WinCC V6.2 +SP2

WinCC V6.0 + SP4 (12/2005) **6AV6381-1B*06-0EX0** **released for Windows 2000 + SP4 (Professional / Server / Advanced Server), Windows XP Professional + SP1/2 and Windows Server 2003, Server 2003 + SP1**		**WinCC communication chanel**							
		SIMATIC S7 Protocol Suite		**SIMATIC S5**				**SIMATIC 505**	
				TF	**Layer 4**		**PMC[1)]**		
		ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP
SIMATIC NET --- CD: Edition 2005 +HF1 (07/2005)									
CP 1612 (The software SOFTNET-S7 must be order seperatly)	6GK1161-2AA00	X	X			X			X_2
SOFTNET-S7 2005 +HF1 released for Windows 2000 (Professional/Server), Windows XP Professional and Windows 2003 Server	6GK1704-1CW63-3AA0	X_3	X_3			X_3			
SOFTNET-S7 Lean 2005 +HF1 released for Windows 2000 (Professional/Server), Windows XP Professional and Windows 2003 Server	6GK1704-1LW63-3AA0	X	X			X			
CP 1613 A2 (Communication software S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA01	X	X		X	X	X	X	X_2
S7-1613 2005 +HF1 released for Windows 2000 (Professional/Server), Windows XP Professional and Windows 2003 Server	6GK1716-1CB63-3AA0	X_3	X_3		X_3	X_3	X_3	X_3	
TF-1613 2005 +HF1 released for Windows 2000 (Professional/Server) and Windows XP Professional	6GK1716-1TB63-3AA0			X_3	X_3	X_3	X_3	X_3	

x = SIMATIC NET products are tested and released with WinCC

= please see the operating system restriction from WinCC / NET

1) S5-PMC as ADD ON from CC Erlangen

2) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily

3) SIMATIC NET driver for Windows 2000 Advanced Server on request only

WinCC V6.0 + SP3 (03/2005) **released for Windows 2000 + SP3/4 (Professional / Server / Advanced Server), Windows XP Professional + SP1/2 and Windows Server 2003**	**6AV6381-1B*06-0DX0**	**WinCC communication chanel**							
		SIMATIC S7 Protocol Suite		**SIMATIC S5**				**SIMATIC 505**	
				TF	**Layer 4**		**PMC[1)]**		
		ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP
SIMATIC NET --- V6.2 - CD 11/2003 + SP1 (09/2004) **Products**									
CP 1512	6GK1151-2AA00	X	X			X			X_2
CP 1612 (The software SOFTNET-S7 must be order seperatly)	6GK1161-2AA00	X	X			X			X_2
SOFTNET-S7 V6.2 (CD 11/2003 + SP1) released for Windows 2000 (Professional/Server), Windows XP Professional and Windows 2003 Server	6GK1704-1CW62-3AA0	X_3	X_3			X_3			
SOFTNET-S7 Lean V6.2 (CD 11/2003 + SP1) released for Windows 2000 (Professional/Server), Windows XP Professional and Windows 2003 Server	6GK1704-1LW62-3AA0	X	X			X			
CP 1613 (Communication software S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA00	X	X		X	X	X	X	X_2
CP 1613 A2 (communication software S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA01	X	X		X	X	X	X	X_2
S7-1613 V6.2 (CD 11/2003 + SP1) released for Windows 2000 (Professional/Server), Windows XP Professional and Windows 2003 Server	6GK1716-1CB62-3AA0	X_3	X_3		X_3	X_3	X_3	X_3	
TF-1613 V6.2 (CD 11/2003 + SP1) released for Windows 2000 (Professional/Server)	6GK1716-1TB62-3AA0			X_3	X_3	X_3	X_3	X_3	

x = SIMATIC NET products are tested and released with WinCC

= please see the operating system restriction from WinCC / NET

1) S5-PMC as ADD ON from CC Erlangen
2) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily

3) SIMATIC NET driver for Windows 2000 Advanced Server on request only

WinCC V6.0 + SP2 (05/2004) **released for Windows 2000 + SP3/4 (Professional / Server / Advanced Server), Windows XP Professional + SP1 and Windows Server 2003**	**6AV6381-1B*06-0CX0**	**WinCC communication chanel**							
		SIMATIC S7 Protocol Suite		**SIMATIC S5**				**SIMATIC 505**	
				TF	**Layer 4**		**PMC[1)]**		
		ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP
SIMATIC NET Products --- V6.2 - CD 11/2003 (01/2004)									
CP 1512 (The software SOFTNET-S7 must be order seperatly)	6GK1151-2AA00	X	X			X			X_2
CP 1612 (The software SOFTNET-S7 must be order seperatly)	6GK1161-2AA00	X	X			X			X_2
SOFTNET-S7 V6.2 (CD 11/2003) released for Windows 2000 (Professional/Server), Windows XP Professional and Windows 2003 Server	6GK1704-1CW62-3AA0	X_3	X_3			X_3			
SOFTNET-S7 Lean V6.2 (CD 11/2003) released for Windows 2000 (Professional/Server), Windows XP Professional and Windows 2003 Server	6GK1704-1LW62-3AA0	X	X			X			
CP 1613 (Communication software S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA00	X	X		X	X	X	X	X_2
CP 1613 A2 (Communication software S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA01		X_4						X_2
S7-1613 V6.2 (CD 11/2003) released for Windows 2000 (Professional/Server), Windows XP Professional and Windows 2003 Server	6GK1716-1CB62-3AA0	X_3	X_3		X_3	X_3	X_3	X_3	
TF-1613 V6.2 (CD 11/2003) released for Windows 2000 (Professional/Server)	6GK1716-1TB62-3AA0			X_3	X_3	X_3	X_3	X_3	

X = SIMATIC NET products are tested and released with WinCC

1) S5-PMC as ADD ON from CC Erlangen

2) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily

3) SIMATIC NET driver for Windows 2000 Advanced Server on request only

4) CP1613 A2 is only released with Simatic NET V6.2 if you use the TCP/IP driver from the hardware package

WinCC V6.0 + SP1 (09/2003) **released for Windows 2000 + SP2/3 (Professional / Server / Advanced Server) and Windows XP Professional + SP1**	**6AV6381-1B*06-0BX0**	**WinCC communication chanel**							
		SIMATIC S7 Protocol Suite		**SIMATIC S5**				**SIMATIC 505**	
				TF	**Layer 4**		**PMC[1)]**		
		ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP
SIMATIC NET --- V6.1 - CD 11/2002 + SP1 (08/2003)									
CP 1512	6GK1151-2AA00	X	X			X			X_2
CP 1612 (The software SOFTNET-S7 must be order seperatly)	6GK1161-2AA00	X	X			X			X_2
SOFTNET-S7 V6.1 (CD 11/2002 + SP1) released for Windows 2000 (Professional/Server) and Windows XP Professional	6GK1704-1CW61-3AA0	X_3	X_3			X_3			
SOFTNET-S7 Lean V6.1 (CD 11/2002 + SP1) released for Windows 2000 (Professional/Server) and Windows XP Professional	6GK1704-1LW61-3AA0	X	X			X			
CP 1613 (Communication software S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA00	X	X		X	X	X	X	X_2
S7-1613 V6.1 (CD 11/2002 + SP1) released for Windows 2000 (Professional/Server) and Windows XP Professional	6GK1716-1CB61-3AA0	X_3	X_3		X_3	X_3	X_3	X_3	
TF-1613 V6.1 (CD 11/2002 + SP1) released for Windows 2000 (Professional/Server)	6GK1716-1TB61-3AA0			X_3	X_3	X_3	X_3	X_3	

x = SIMATIC NET products are tested and released with WinCC

= please see the operating system restriction from WinCC / NET

1) S5-PMC as ADD ON from CC Erlangen
2) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily
3) SIMATIC NET driver for Windows 2000 Advanced Server on request only

WinCC V6.0 6AV6381-1B*06-1AX0 released for Windows 2000 + SP3 (Professional / Server / Advanced Server) and Windows XP		**WinCC communication chanel**							
		SIMATIC S7 Protocol Suite		**TF**	**SIMATIC S5 Layer 4**		**PMC[1)]**	**SIMATIC 505**	
		ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP
SIMATIC NET --- V6.0 - CD 07/2001 + SP5 (11/2002)									
CP 1512 (The software SOFTNET-S7 must be order seperatly)	6GK1151-2AA00	X	X			X		X	X_2
CP 1612 (The software SOFTNET-S7 must be order seperatly)	6GK1161-2AA00	X	X			X		X	X_2
SOFTNET-S7 V6.0 (CD 07/2001 + SP5) released for Windows NT 4.0 (Workstat. / Server) + SP6a and Windows 2000 (Professional/Server) + SP 1/2/3	6GK1704-1CW61-3AA0	X_3	X_3			X_3		X_3	
SOFTNET-S7 V6.1 (CD 11/2002 + SP1)	6GK1704-1CW61-3AA0	X	X			X		X	
CP 1613 (communications software S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA00	X	X		X	X	X	X	X_2
S7-1613 V6.0 (CD 07/2001 + SP5) released for Windows NT 4.0 (Workstat. / Server) + SP6a and Windows 2000 (Professional/Server) + SP 1/2/3	6GK1716-1CB61-3AA0	X_3	X_3		X_3	X_3	X_3	X_3	
S7-1613 V6.1 (CD 11/2002 + SP1) released for Windows XP + SP1	6GK1716-1CB61-3AA0	X	X		X	X	X	X	
TF-1613 V6.0 (CD 07/2001 + SP5) released for Windows NT 4.0 (Workstat. / Server) + SP6a and Windows 2000 (Professional/Server) + SP 1/2/3	6GK1716-1TB60-3AA0			X_3	X_3	X_3	X_3	X_3	

x = SIMATIC NET products are tested and released with WinCC

1) S5-PMC as ADD ON from CC Erlangen
2) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily
3) SIMATIC NET driver for Windows 2000 Advanced Server on request only

WinCC V5.1 + SP2 (06/2004) **6AV6381-1B*05-1CX0** **released for Windows NT 4.0 + SP6a/6a+SRP (Workstat. / Server) and Windows 2000 + SP2/3/4 (Professional / Server / Advanced Server)**		**WinCC communication chanel**							
		SIMATIC S7 Protocol Suite		**SIMATIC S5**				**SIMATIC 505**	
				TF	**Layer 4**		**PMC**		
		ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP
SIMATIC NET --- V6.2 - CD 11/2003 (01/2004)									
CP 1512 (The software SOFTNET-S7 must be order seperatly)	6GK1151-2AA00	X	X			X			X_1
CP 1612 (The software SOFTNET-S7 must be order seperatly)	6GK1161-2AA00	X	X			X			X_1
SOFTNET-S7 V6.2 (CD 11/2003) released for Windows 2000 (Professional/Server), Windows XP Professional and Windows 2003 Server	6GK1704-1CW62-3AA0	X_2	X_2			X_2			
SOFTNET-S7 V6.0 (CD 07/2001 + SP5+HF2) released for Windows NT 4.0 (Workstat. / Server)	6GK1704-1CW60-3AA0	X	X			X			
SOFTNET-S7 Lean V6.2 (CD 11/2003) released for Windows 2000 (Professional/Server), Windows XP Professional and Windows 2003 Server	6GK1704-1LW62-3AA0	X_2	X_2			X_2			
CP 1613 (Communication software S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA00	X	X		X	X	X	X	X_1
CP 1613 A2 (Communiaction software S7-1613 must be order seperatly)	6GK1161-3AA01		X_3						X_1
S7-1613 V6.2 (CD 11/2003) released for Windows 2000 (Professional/Server), Windows XP Professional and Windows 2003 Server	6GK1716-1CB62-3AA0	X_2	X_2		X_2	X_2	X_2	X_2	
S7-1613 V6.0 (CD 07/2001 + SP5+HF2) released for Windows NT 4.0 (Workstat. / Server)	6GK1716-1CB60-3AA0	X	X		X	X	X	X	
TF-1613 V6.1 (CD 11/2003) released for Windows 2000 (Professional/Server)	6GK1716-1TB61-3AA0			X_2	X_2	X_2	X_2	X_2	
TF-1613 V6.0 (CD 07/2001 + SP5+HF2) released for Windows NT 4.0 (Workstat. / Server)	6GK1716-1TB60-3AA0			X	X	X	X	X	

x = SIMATIC NET products are tested and released with WinCC

= please see the operating system restriction from WinCC / NET

1) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily
2) SIMATIC NET driver for Windows 2000 Advanced Server on request only
3) CP1613 A2 is only released with Simatic NET V6.2 if you use the TCP/IP driver from the hardware package

WinCC V5.1 + SP1 (10/2003) released for Windows NT 4.0 + SP6a/6a+SRP (Workstat. / Server) and Windows 2000 + SP2/3/4 (Professional / Server / Advanced Server)	**6AV6381-1B*05-1BX0**	**WinCC communication chanel**							
		SIMATIC S7 Protocol Suite		**SIMATIC S5**				**SIMATIC 505**	
				TF	**Layer 4**		**PMC**		
		ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP
SIMATIC NET --- V6.1 - CD 11/2002 + SP1 (08/2003) **Products --- V6.0 - CD 07/2001 + SP5+HF2 (08/2003)**									
CP 1512 (The software SOFTNET-S7 must be order seperatly)	6GK1151-2AA00	X	X			X			X_1
CP 1612 (The software SOFTNET-S7 must be order seperatly)	6GK1161-2AA00	X	X			X			X_1
SOFTNET-S7 V6.1 (CD 11/2002 + SP1) released for Windows 2000 (Professional/Server) and Windows XP Professional	6GK1704-1CW61-3AA0	X_2	X_2			X_2			
SOFTNET-S7 V6.0 (CD 07/2001 + SP5+HF2) released for Windows NT 4.0 (Workstat. / Server)	6GK1704-1CW60-3AA0	X_2	X_2			X_2			
SOFTNET-S7 Lean V6.1 (CD 11/2002 + SP1) released for Windows 2000 (Professional/Server) and Windows XP Professional	6GK1704-1LW61-3AA0	X	X			X			
CP 1613 (Communication software S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA00	X	X		X	X	X	X	X_1
S7-1613 V6.1 (CD 11/2002 + SP1) released for Windows 2000 (Professional/Server) and Windows XP Professional	6GK1716-1CB61-3AA0	X_2	X_2		X_2	X_2	$X_{2,3}$	X_2	
S7-1613 V6.0 (CD 07/2001 + SP5+HF2) released for Windows NT 4.0 (Workstat. / Server)	6GK1716-1CB60-3AA0	X_2	X_2		X_2	X_2	X_2	X_2	
TF-1613 V6.1 (CD 11/2002 + SP1) released for Windows 2000 (Professional/Server)	6GK1716-1TB61-3AA0			X_2	X_2	X_2	X_2	X_2	
TF-1613 V6.0 (CD 07/2001 + SP5+HF2) released for Windows NT 4.0 (Workstat. / Server)	6GK1716-1TB60-3AA0			X_2	X_2	X_2	X_2	X_2	

x = SIMATIC NET products are tested and released with WinCC

1) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily
2) SIMATIC NET driver for Windows 2000 Advanced Server on request only

WinCC V5.1 (02/2002) released for Windows NT 4.0+ SP6a (Workst./Server) and Windows 2000 + SP2 (Professional / Server / Advanced Server)	**6AV6381-1B*05-1AX0**	**WinCC communication chanel**							
		SIMATIC S7 Protocol Suite		**SIMATIC S5**				**SIMATIC 505**	
				TF	**Layer 4**		**PMC[1)]**		
		ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP
SIMATIC NET --- V6.0 - CD 07/2001 + SP4 (04/2002)									
CP 1512 (The software SOFTNET-S7 must be order seperatly)	6GK1151-2AA00	X	X			X		X	X_2
CP 1612 (The software SOFTNET-S7 must be order seperatly)	6GK1161-2AA00	X	X			X		X	X_2
SOFTNET-S7 V6.0 (CD 07/2001 + SP5) released for Windows NT 4.0 (Workstat. / Server) and Windows 2000 (Professional/Server)	6GK1704-1CW61-3AA0	X_3	X_3			X_3		X_3	
CP 1613 (communications software S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA00	X	X		X	X	X	X	X_2
S7-1613 V6.0 (CD 07/2001 + SP5) released for Windows NT 4.0 (Workstat. / Server) and Windows 2000 (Professional/Server)	6GK1716-1CB61-3AA0	X_3	X_3		X_3	X_3	X_3	X_3	
TF-1613 V6.0 (CD 07/2001 + SP5) released for Windows NT 4.0 (Workstat. / Server) and Windows 2000 (Professional/Server)	6GK1716-1TB60-3AA0			X_3	X_3	X_3	X_3	X_3	

x = SIMATIC NET products are tested and released with WinCC

1) S5-PMC as ADD ON from CC Erlangen
2) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily
3) SIMATIC NET driver for Windows 2000 Advanced Server on request only

WinCC V5.0 + SP2 (02/2001) **6AV6381-1B*05-0CX0** **released for Windows NT 4.0 + SP5/6a (Workstat. / Server) and Windows 2000 + SP1 (Professional / Server / Advanced Server)**		**WinCC communication chanel**							
		SIMATIC S7 Protocol Suite		**SIMATIC S5**				**SIMATIC 505**	
				TF	**Layer 4**		**PMC**		
		ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP
SIMATIC NET Products - CD 05/2000									
CP 1411 (The software SOFTNET-S7 must be order seperatly)	6GK1141-1AA00	X	X			X			X_1
CP 1511 (The software SOFTNET-S7 must be order seperatly)	6GK1151-1AA00	X	X			X			X_1
SOFTNET-S7 V3.3 released for Windows 98 , NT 4.0 (Workstat. / Server) and Windows 2000 (Professional)	6GK1704-1CW33-3AA0	X_2	X_2			X			
CP 1613 (Communication software S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA00	X	X		X	X	X	X	X_1
S7-1613 V2.1 released for Windows NT 4.0 (Workstat. / Server) and Windows 2000 (Professional)	6GK1716-1CB21-3AA0	X_2	X_2		X_2	X_2	X_2	X_2	
TF-1613 V2.1 released for Windows NT 4.0 (Workstat. / Server) and Windows 2000 (Professional)	6GK1716-1TB21-3AA0			X	X	X	X	X	
S7-NET1413 (Package: CP 1413 + S7-1413) released for Windows 98, NT 4.0 (Workstat. / Server)	6GK1141-3CW52	X	X		X	X	X	X	X_1
TF-NET1413 (Package: CP 1413 + TF-1413) released for Windows 98, NT 4.0 (Workstat. / Server)	6GK1141-3TW52			X	X	X	X	X	X_1
S7-1413 V5.2 + SP2 released for Windows 98, NT 4.0 (Workstat. / Server)	6GK1701-1CW52-3AA0	X	X		X	X	X	X	
TF-1413 V5.2 + SP2	6GK1701-1TW52-3AA0			X	X	X	X	X	

x = SIMATIC NET products are tested and released with WinCC

= please see the operating system restriction from WinCC / NET

1) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily

2) SIMATIC NET -released for Windows 2000 + SP1 (Professional / Server / Advanced Server) only with the installation guide (Attachment 1)

WinCC V5.0 + SP1 (04/2000) released for Windows NT 4.0 + SP3/4/5/6a (Workstat. / Server)	**6AV6381-1B*05-0BX0**	**WinCC communication chanel**							
		SIMATIC S7 Protocol Suite		**TF**	**SIMATIC S5 Layer 4**		**PMC**	**SIMATIC 505**	
		ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP	ISO_L4	ISO_L4	TCP/IP
SIMATIC NET Products (CD 11/1999)									
CP 1411 (The software SOFTNET-S7 must be order seperatly)	6GK1141-1AA00	X	X			X			X_1
CP 1511 (The software SOFTNET-S7 must be order seperatly)	6GK1151-1AA00	X	X			X			X_1
SOFTNET-S7 V3.2 released for Windows 98 and NT 4.0 (Workstat. / Server)	6GK1704-1CW32-3AA0	X	X			X			
CP 1613 (Communication software S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA00	X	X		X	X	X	X	X_1
S7-1613 V2.0 released for Windows NT 4.0 (Workstat. / Server)	6GK1716-1CB20-3AA0	X_2	X_2		X_2	X_2	X_2	X_2	
TF-1613 V2.0 released for Windows NT 4.0 (Workstat. / Server)	6GK1716-1TB20-3AA0				X_2	X_2	X_2	X_2	
S7-NET1413 (Package: CP 1413 + S7-1413) released for Windows 98 and NT 4.0 (Workstat. / Server)	6GK1141-3CW52	X	X		X	X	X	X	X_1
TF-NET1413 (Package: CP 1413 + TF-1413) released for Windows 98 and NT 4.0 (Workstat. / Server)	6GK1141-3TW52			X	X	X	X	X	X_1
S7-1413 V5.2	6GK1701-1CW52-3AA0	X	X		X	X	X	X	
TF-1413 V5.2 released for Windows 98 and NT 4.0 (Workstat. / Server)	6GK1701-1TW52-3AA0			X	X	X	X	X	

x = SIMATIC NET products are tested and released with WinCC

= please see the operating system restriction from WinCC / NET

1) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily

2) Funktioniert nur, wenn zuvor einmal die Installationsroutine für S7-1413 oder TF-1413 durchlaufen wurde

WinCC V5.0 (08/1999) released for Windows NT 4.0 + SP5/6a (Workstat. / Server)	**6AV6381-1B*05-0AX0**	**WinCC communication chanel**						
		SIMATIC S7 Protocol Suite		**SIMATIC S5**			**SIMATIC 505**	
				TF	**Layer 4**	**PMC**		
		ISO_L4	TCP/IP	ISO_L4	ISO_L4	ISO_L4	ISO_L4	TCP/IP
SIMATIC NET products (CD 05/1999)								
CP 1411 (The software SOFTNET-S7 must be order seperatly)	6GK1141-1AA00	X	X				X	X[1]
CP 1511 (The software SOFTNET-S7 must be order seperatly)	6GK1151-1AA00	X	X				X	X[1]
SOFTNET-S7 V3.0 released for Windows 98 and NT 4.0 (Workstat. / Server)	6GK1704-1CW31-3AA0	X	X				X	
S7-NET1413 (Paket: CP 1413 + S7-1413) released for Windows 98 and NT 4.0 (Workstat. / Server)	6GK1141-3CW51	X	X		X	X	X	X[1]
TF-NET1413 (Paket: CP 1413 + TF-1413) released for Windows 98 and NT 4.0 (Workstat. / Server)	6GK1141-3TW51			X	X	X	X	X[1]
S7-1413 V5.1	6GK1701-1CW51-3AA0	X	X		X	X	X	
TF-1413 V5.1 released for Windows 98 and NT 4.0 (Workstat. / Server)	6GK1701-1TW51-3AA0			X	X	X	X	

x = SIMATIC NET products are tested and released with WinCC

= please see the operating system restriction from WinCC / NET

1) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily

WinCC V4.02 + SP3 (04/2001) released for Windows 95/98 and Windows NT 4.0 + SP3/4/5/6a (Workstat. / Server)	**6AV6381-1B*04-0EX0**	**WinCC communication chanel**						
		SIMATIC S7 Protocol Suite		**SIMATIC S5**			**SIMATIC 505**	
				TF	**Layer 4**	**PMC**		
		ISO_L4	TCP/IP	ISO_L4	ISO_L4	ISO_L4	ISO_L4	TCP/IP
SIMATIC NET products (CD 05/2000)								
CP 1411 (The software SOFTNET-S7 must be order seperatly)	6GK1141-1AA00	X	X				X	X_1
CP 1511 (The software SOFTNET-S7 must be order seperatly)	6GK1151-1AA00	X	X				X	X_1
SOFTNET-S7 V3.3 released for Windows 98 , NT 4.0 (Workstat. / Server) and Windows 2000 (Professional)	6GK1704-1CW33-3AA0	X	X				X	
CP 1613 (Communication software S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA00	X	X		X	X	X	X_1
S7-1613 V2.1 released for Windows NT 4.0 (Workstat. / Server) and Windows 2000 (Professional)	6GK1716-1CB21-3AA0	X	X		X	X	X	
TF-1613 V2.1 released for Windows NT 4.0 (Workstat. / Server) and Windows 2000 (Professional)	6GK1716-1TB21-3AA0				X	X	X	
S7-NET1413 (Paket: CP 1413 + S7-1413) released for Windows 98 , NT 4.0 (Workstat. / Server)	6GK1141-3CW52	X	X		X	X	X	X_1
TF-NET1413 (Paket: CP 1413 + TF-1413) released for Windows 98 , NT 4.0 (Workstat. / Server)	6GK1141-3TW52			X	X	X	X	X_1
S7-1413 V5.2 + SP2 released for Windows 98 , NT 4.0 (Workstat. / Server)	6GK1701-1CW52-3AA0	X	X		X	X	X	
TF-1413 V5.2 + SP2 released for Windows 98 , NT 4.0 (Workstat. / Server)	6GK1701-1TW52-3AA0			X	X	X	X	

x = SIMATIC NET products are tested and released with WinCC

= please see the operating system restriction from WinCC / NET

1) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily

WinCC V4.02 + SP2 (10/2000) released for Windows 95/98 and Windows NT 4.0 + SP3/4/5/6a (Workstat. / Server)	**6AV6381-1B*04-0DX0**	**WinCC communication chanel**						
		SIMATIC S7 Protocol Suite		**SIMATIC S5**			**SIMATIC 505**	
				TF	**Layer 4**	**PMC**		
		ISO_L4	TCP/IP	ISO_L4	ISO_L4	ISO_L4	ISO_L4	TCP/IP
SIMATIC NET products (CD 05/2000)								
CP 1411 (The software SOFTNET-S7 must be order seperatly)	6GK1141-1AA00	X	X				X	X1
CP 1511 (The software SOFTNET-S7 must be order seperatly)	6GK1151-1AA00	X	X				X	X1
SOFTNET-S7 V3.3 released for Windows 98 , NT 4.0 (Workstat. / Server) and Windows 2000 (Professional)	6GK1704-1CW33-3AA0	X	X				X	
CP 1613 (Communication software S7-1613 or TF-1613 must be order seperatly)	6GK1161-3AA00	X	X		X	X	X	X1
S7-1613 V2.1 released for Windows NT 4.0 (Workstat. / Server) and Windows 2000 (Professional)	6GK1716-1CB21-3AA0	X	X		X	X	X	
TF-1613 V2.1 released for Windows NT 4.0 (Workstat. / Server) and Windows 2000 (Professional)	6GK1716-1TB21-3AA0				X	X	X	
S7-NET1413 (Paket: CP 1413 + S7-1413) released for Windows 98 , NT 4.0 (Workstat. / Server)	6GK1141-3CW52	X	X		X	X	X	X1
TF-NET1413 (Paket: CP 1413 + TF-1413) released for Windows 98 , NT 4.0 (Workstat. / Server)	6GK1141-3TW52			X	X	X	X	X1
S7-1413 V5.2 + SP2 released for Windows 98 , NT 4.0 (Workstat. / Server)	6GK1701-1CW52-3AA0	X	X		X	X	X	
TF-1413 V5.2 + SP2 released for Windows 98 , NT 4.0 (Workstat. / Server)	6GK1701-1TW52-3AA0			X	X	X	X	

x = SIMATIC NET products are tested and released with WinCC

= please see the operating system restriction from WinCC / NET

1) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily

WinCC V4.02 + SP1 (07/1999) released for Windows 95/98 and Windows NT 4.0 + SP3/4/5 (Workstat. / Server)	**6AV6381-1B*04-0CX0**	**WinCC communication chanel**						
		SIMATIC S7 Protocol Suite		**SIMATIC S5**			**SIMATIC 505**	
				TF	**Layer 4**	**PMC**		
		ISO_L4	TCP/IP	ISO_L4	ISO_L4	ISO_L4	ISO_L4	TCP/IP
SIMATIC NET products (CD 05/1999)								
CP 1411 (The software SOFTNET-S7 must be order seperatly)	6GK1141-1AA00	X	X				X	X_1
CP 1511 (The software SOFTNET-S7 must be order seperatly)	6GK1151-1AA00	X	X				X	X_1
SOFTNET-S7 V3.0 released for Windows 98 and NT 4.0 (Workstat. / Server)	6GK1704-1CW31-3AA0	X	X				X	
S7-NET1413 (Paket: CP 1413 + S7-1413) released for Windows 98 and NT 4.0 (Workstat. / Server)	6GK1141-3CW51	X	X		X	X	X	X_1
TF-NET1413 (Paket: CP 1413 + TF-1413) released for Windows 98 and NT 4.0 (Workstat. / Server)	6GK1141-3TW51			X	X	X	X	X_1
S7-1413 V5.1 released for Windows 98 and NT 4.0 (Workstat. / Server)	6GK1701-1CW51-3AA0	X	X		X	X	X	
TF-1413 V5.1 released for Windows 98 and NT 4.0 (Workstat. / Server)	6GK1701-1TW51-3AA0			X	X	X	X	

x = SIMATIC NET products are tested and released with WinCC

= please see the operating system restriction from WinCC / NET

1) Possible to use Interface-Board with NDIS 3.0 - Interface ; no communications software are necessarily