

RESOLUTION MEPC.197(62)

FORM OF MATERIAL DECLARATION

<Date of declaration>

Date 24.02.2015

<MD ID number>

MD-ID-No. IW-15Z09

<Other information>

Remark 1	
Remark 2	
Remark 3	

<Supplier (respondent) information>

Company name	Siemens AG
Division name	PD
Address	Vogelweiherstr. 1-15, 90441 Nuremberg, Germany
Contact person	Martin Sacherl
Telephone number	+ 49 911 433-6342
Fax number	+ 49 911 433-7095
E-mail address	martin.sacherl@siemens.com
SDoC ID no.:	IW-15Z10

<Product information>

Product name	Product number	Delivered unit		Product Information
		Amount	Unit	
SINAMICS S120 Chassis, flüssigkeitsgekühlt	6SL3305-7TExX-X..., 6SL3305-7TGXX-X..., 6SL3315-1TExX-X..., 6SL3335-1TExX-X..., 6SL3335-1TGXX-X..., 6SL3335-7TExX-X..., 6SL3335-7TGXX-X..., 6SL3325-1TExX-X..., 6SL3325-1TGXX-X...	1	filter	

<Materials information>

This materials information shows the amount of hazardous materials contained in

1	Unit piece
---	---------------

 (unit: piece, kg, m, m², m³, etc) of the product


Table	Material name		Threshold level	Present above threshold level	If yes, material mass		If yes, information on where it is used
				Yes/No	Mass	Unit	
Table A (materials listed in Appendix 1 of the Convention)	Asbestos	Asbestos	No threshold level	No			
	Poly chlorinated	Polychlorinated biphenyls (PCBs)	No threshold level	No			
	Ozone depleting substance	Chlorofluorocarbons (CFCs)	no threshold level	No			
		Halons		No			
		Other fully halogenated CFCs		No			
		Carbon tetrachloride		No			
		1,1,1-Trichloroethane		No			
		Hydrochlorofluorocarbons		No			
		Hydrobromofluorocarbons		No			
		Methyl bromide		No			
		Bromochloromethane		No			
	Anti-fouling systems containing organotin compounds as a biocide		2,500 mg total tin/kg	No			
				No			
				No			

Table	Material name		Threshold level	Present above threshold level	If yes, material mass		If yes, information on where it is used
				Yes/No	Mass	Unit	
Table b (materials listed in appendix 2 of the Convention)	Cadium and cadium compounds		100 mg/kg	No			
	Hexavalent chromium and hexavalent chromium compounds		1,000 mg/kg	Yes	80	mg	Total amount in the product. Surface treatment for screws to prevent corrosion. The content of Cr VI in the surface treatment is approx. 29 %
	Lead and lead compounds		1,000 mg/kg	Yes	192,066	mg	Maximum amount in the product, contained in IGBTs.
	Mercury and mercury compounds		1,000 mg/kg	No			
	Polybrominated biphenyl (PBBs)		1,000 mg/kg	No			
	Polybrominated dephenyl ethers (PBDEs)		1,000 mg/kg	No			
	Polychloronaphthalenes (Cl >=3)		no threshold level	No			
	Radioactive substances		no threshold level	No			
	Certain shortchain chlorinated parafins		1%	No			

We hereby confirm that the products we deliver are declared to our best knowledge.


Signature

Hr. Dr. Sommer, Rainer, PD LD P R&D 1
Head R&D Drives


Signature

Hr. Dr. Hassmann, Joerg, PD LD P PPM
Head Product Management