



Certificate of Compliance

Certificate: 70010419 **Master Contract:** 165071 (012730_C_000)
Project: 70109347 **Date Issued:** 2017-08-10
Issued to: Siemens AG
DF CP R&D VC 2
Werner-von-Siemens-Strasse 48
Amberg, 92224
GERMANY

The products listed below are eligible to bear the CSA Mark shown



Issued by: Steven Montminy
Steven Montminy

PRODUCTS

CLASS - C321103 - INDUSTRIAL CONTROL EQUIPMENT-Motor Controllers - Auxiliary Devices
CLASS - C321123 - INDUSTRIAL CONTROL EQUIPMENT-Motor Controllers-Auxiliary Devices-

Complete devices, open type:

Pushbutton, non-illuminated, Cat. No. 3SU11 followed by 0, 3, 5 or 6, followed by 0, followed by 0A, 0B, 0C, 0D, 0J or 0K, followed by A or B, followed by 00 up to 80, followed by 1 or 3, followed by B, C, F, L, M, N, P or other letter, followed by A, B, C, D, F, G, H, J, K, M, N, P, Q, R or other letter

Pushbutton, illuminated, Cat. No. 3SU11 followed by 0, 3, 5 or 6, followed by 2, 3 or 6, followed by 0A, 0B, 0C, 0D, 0J or 0K, followed by A, B or D, followed by 00 up to 80, followed by 0, 1 or 3, followed by A, B, C, F, L, M, N, P or other letter, followed by A, B, C, D, F, G, H, J, K, M, N, P, Q, R or other letter

Pushbutton, stop, Cat. No. 3SU11 followed by 0, 3, 5 or 6, followed by 0, followed by 0H, followed by C, followed by 10 or 20, followed by 1 or 3, followed by B, C, F, L, M, N, P or other letter, followed by A, B, C, D, F, G, H, J, K, M, N, P, Q, R or other letter

Mushroom pushbutton, Cat. No. 3SU11 followed by 0, 3, 5 or 6, followed by 0, followed by 1A, 1B, 1C or 1E, followed by A or D, followed by 00 up to 70, followed by 1 or 3, followed by B, C, F, L, M, N, P or other letter, followed by A, B, C, D, F, G, H, J, K, M, N, P, Q, R or other letter

Mushroom pushbutton, illuminated, Cat. No. 3SU11 followed by 0, 3, 5 or 6, followed by 2, 3 or 6, followed by 1A, 1B, 1C or 1E, followed by A or D, followed by 00 up to 70, followed by 0, 1 or 3, followed by A, B, C, F, L, M, N, P or other letter, followed by A, B, C, D, F, G, H, J, K, M, N, P, Q, R or other letter



Certificate: 70010419

Master Contract: 165071

Project: 70109347

Date Issued: 2017-08-10

Mushroom pushbutton, e-stop, Cat. No. 3SU11 followed by 0, 3, 5 or 6, followed by 0, followed by 1G, 1H or 1J, followed by A, B, F, G, H, K, M, N, Q, R, S, T, U, V or X, followed by 10, 20, 30 or 50, followed by 1 or 3, followed by B, C, F, L, M, N, P or other letter, followed by A, B, C, D, F, G, H, J, K, M, N, P, Q, R or other letter

Mushroom pushbutton, illuminated e-stop, Cat. No. 3SU11 followed by 0, 3, 5 or 6, followed by 2, 3 or 6, followed by 1G, 1H or 1J, followed by B, followed by 20, followed by 0, 1 or 3, followed by A, B, C, F, L, M, N, P or other letter, followed by A, B, C, D, F, G, H, J, K, M, N, P, Q, R or other letter

Selector switch, Cat. No. 3SU11 followed by 0, 3, 5 or 6, followed by 0, 2, 3 or 6, followed by 2A, 2B, 2C, 2D, 2E or 2F, followed by C, F, L, M, N or P, followed 00 up to 70, followed by 1 or 3, followed by B, C, F, L, M, N, P or other letter, followed by A, B, C, D, F, G, H, J, K, M, N, P, Q, R or other letter

Pushbutton, twin non-illuminated, Cat. No. 3SU11 followed by 0, 3, 5 or 6, followed by 0, followed by 3A or 3B, followed by B, followed by 00 up to 70, followed by 1 or 3, followed by B, C, F, L, M, N, P or other letter, followed by A, B, C, D, F, G, H, J, K, M, N, P, Q, R or other letter

Pushbutton, twin illuminated, Cat. No. 3SU11 followed by 0, 3, 5 or 6, followed by 2, 3, 6, 7 or 8, followed by 3A or 3B, followed by B, followed 00 up to 70, followed by 0, 1 or 3, followed by A, B, C, F, L, M, N, P or other letter, followed by A, B, C, D, F, G, H, J, K, M, N, P, Q, R or other letter

Pushbutton, extended, complete devices Cat. No. 3SU12 followed by 0, 3 or 5, followed by 0 or 1, followed by 0, followed by F or E, followed by B, followed by 0AA0, may be followed by letters and/or numbers, followed by 1 or 3, followed by B, C, F, L, M, N, P or other letter, followed by A, B, C, D, F, G, H, J, K, M, N, P, Q, R or other letter

Toggle switch, Cat. No. 3SU11 followed by 0, 3, 5 or 6, followed by 0, followed by 3E, followed by A or C, followed by 10, followed by 1 or 3, followed by B, C, F, L, M, N, P or other letter, followed by A, B, C, D, F, G, H, J, K, M, N, P, Q, R or other letter

Key switch/ con, Cat. No. 3SU11 followed by 0, 3, 5 or 6, followed by 0, followed by 4A, 4B, 4C, 4D, 4F, 4G, 4H 4J, 4L, 5B, 5H, 5J, 5K, 5L, 5P, 5Q, 5R, 5S, 5T or 5X, followed by C, F, L, N, M or P, followed by 01, 11, 21, 31, 41, 51 or 61, followed by 1 or 3, followed by B, C, F, L, M, N, P or other letter, followed by A, B, C, D, F, G, H, J, K, M, N, P, Q, R or other letter

Devices supplied as complete factory-assembled in 3SU1 series, or may be provided separately with accessories:
Pushbutton, extended Cat. No. 3SU12 followed by 0, 3 or 5, followed by 0 or 1, followed by 0, followed by E or F, followed by B, followed by 0AA0, may be followed by letters and/or numbers for manufactures use

Holders Cat No. 3SU15 followed by 0 or 5, followed by 0 or 1, followed by 1A, followed by A or G, followed by 00 up to 60, followed by 0, 1 or 3 followed by B, C, F, L or N, followed by A, followed by numbers and/or letters
Actuator for Pilot light Cat No. 3SU10.-6A...-0AA. plastic or metal /shiny.

Actuator for Pushbutton, flat or raised, momentary maintained, plastic, metal/plastic, metal/shiny or metal/matt, Cat. No. 3SU10.-0....-0A..

Actuators for Mushroom pushbutton, e-stop, 30 or 40 or 60 mm, plastic or metallic, Cat No. 3SU10.0-1....-0AA.

Actuators for Mushroom pushbutton, illuminated e-stop, 30 or 40 or 60mm, plastic or metallic, Cat No.. 3SU10.1-1....-0AA..

Actuators for Selector switch, Cat No. 3SU10.2-2....-0AA0

Actuators for Key switch, plastic or metallic/plastic or metallic, with lock type Ronis or OMR, Cat No. 3SU10.0-4....-0AA0

Actuators for Key switch, plastic or metallic/plastic or metallic, with lock type BKS or CES or IKON, Cat No. 3SU10.0-5....-0AA0

Actuators for Key switch, metallic/plastic, with key release control, Cat No. 3SU10.0-5J...-0AA0

Holders, 3-positions, plastic or metallic, Cat No. 3SU15.0-0AA10-0AA0



Certificate: 70010419
Project: 70109347

Master Contract: 165071
Date Issued: 2017-08-10

Accessories Cat No. 3SU19 followed by 0, 1, 5 or 6, followed 0 or 1, followed by 0, followed by a combination of two letters, followed by 00 up to 71, followed by 0 and a combination of letters, followed a combination of numbers and/or letter for manufactures use

Plunger Bridges, plastic, Cat. No. 3SU1900-0KC10-0AA0

Key for lock type BKS, Ronis, OMR, CES or IKON, Cat. No. 3SU1950-0F...-0AA0

Stand for two-hand control station, Cat. No. 3SU1950-0HN10-0AA0

Adapter metal shiny for flat Actuators, Cat. No. 3SU1950-0KJ80-0AA0

Adapter 30.5 mm metal matt for Actuators, Cat. No. 3SU1960-0KB10-0AA0

Ratings:

Complete or single devices, contact block: A600, R300

LED module: 24 V ac/dc, 110 V ac, 230 V ac, 6 - 24 V ac/dc, 24 - 240 V ac/dc.

Environmental ratings:

Pilot light, plastic: Types 1, 2, 3, 3R, 4, 4X, 12, 13

Pilot light, metal, metal matt, metal /plastic: Types 1, 2, 3, 3R, 4, 4X, 12, 13

Push button and Mushroom push button, plastic: Types 1, 2, 3, 3R, 4, 4X, 12, 13

Push button and Mushroom push button, metal, metal matt, metal/ plastic: Types 1, 2, 3, 3R, 4, 4X, 12, 13

Selector switch, plastic: Types 1, 2, 3, 3R, 4, 4X 12, 13

Selector switch metal, metal matt, metal/ plastic: Types 1, 2, 3, 3R, 4 4X, 12, 13

Key selector, plastic: Types 1, 2, 3, 3R, 4, 4X, 12, 13

Key selector, metal, metal matt, metal/ plastic: Types 1, 2, 3, 3R, 4, 4X, 12, 13

Mushroom Style Stop, plastic: Types 1, 2, 3, 3R, 4, 4X, 12, 13

Mushroom Style Stop, metal, metal matt, metal/plastic: Types 1, 2, 3, 3R 4, 4X, 12, 13

Twin pushbutton, illuminated: Types 1, 2, 3, 3R, 4, 4X, 12, 13

Push button and Mushroom push button, illuminated: Types 1, 2, 3, 3R, 4, 4X, 12, 13

Pushbutton Stop and Toggle switch: Type 1, 2, 3, 3R, 4, 4X, 12, 13

Adapter 30.5 mm metal matt 3SU1960-0KB10-0AA0/ Shiny 3SU1950-0KB10-0AA0 : Types 1, 2, 3, 3R, 4, 4X, 12 (only when mounted with device/actuator); Adapter 3SU1960-0KB10-0AA0 in use with blanking plug 3SU19...-0F...-0AA.: Type 1 only.

Blanking Plug 3SU19...-0F.80-0AA.. 30.5 mm Type 1, 2, 3, 3R, 4, 4X, 12, 13

Notes:

- Open-type devices are Certified only for use in complete assemblies where the suitability of the combination is subject to further investigation.
- Cat. No. designation may be followed by suffix of numbers and/or letters for manufacturer use only.

APPLICABLE REQUIREMENTS

CSA-C22.2 No. 14-13

CAN/CSA-C22.2 No. 94-M91

CAN/CSA-C22.2 No. 60947-1-13

CAN/CSA-C22.2 No. 60947-5-1-14

Industrial Control Equipment

Special Purpose Enclosures

Low-Voltage Switchgear and Controlgear - Part 1: General rules

Low-voltage switchgear and Controlgear - Part 5-1: Control circuit devices and switching elements - Electromechanical control circuit devices