P1, P2 non FAS-Latch optional fronts

Options: For 24" wide fronts – Add "24" to start of part number: "F44H" becomes "24F44H" Note: 24" wide may require special order in COMPAS for some options.

For Metal Card Holder (stick-on) – Add "M" suffix to end of part number: "F44H" becomes "F44HM"

For Welded Metal Card Holder (special order in COMPAS) – Add "WM" suffix to end of part number: "F44H" becomes "F44HWM"

Front Height Inches	Screw to Box	
	20" W Flush	20" W Surface
	Catalog Number	
26	F26C	S26C
32	F32C	S32C
38	F38C	S38C
44	F44C	S44C
50	F50C	S50C
56	F56C	S56C
62	F62C	S62C
68	F68C	S68C
74	F74C	S74C

Front Height Inches	Hinge to Box	
	20" W Flush	20" W Surface
	Catalog Number	
26	F26H	S26H
32	F32H	S32H
38	F38H	S38H
44	F44H	S44H
50	F50H	S50H
56	F56H	S56H
62	F62H	S62H
68	F68H	S68H
74	F74H	S74H

Front Height Inches	Door-to-Door	
	20" W Flush	20" W Surface
	Catalog Number	
26	F26D	S26D
32	F32D	S32D
38	F38D	S38D
44	F44D	S44D
50	F50D	S50D
56	F56D	S56D
62	F62D	S62D
68	F68D	S68D
74	F74D	S74D




Figure 1: Standard Screw to Box Trim




Figure 2: Standard Hinge to Box




Figure 3: Standard Door in Door

Piano Hinge Options (Stainless 304 is available as option; all have piano hinges)

Front Height Inches	Screw to Box	
	20" W Flush	20" W Surface
	Catalog Number	
26	Ref F26CPH26①	Ref S26CPH26①
32	Ref F32CPH32①	Ref S32CPH32①
38	Ref F38CPH38①	Ref S38CPH38①
44	Ref F44CPH44①	Ref S44CPH44①
50	Ref F50CPH50①	Ref S50CPH50①
56	Ref F56CPH56①	Ref S56CPH56①
62	Ref F62CPH62①	Ref S62CPH62①
68	Ref F68CPH68①	Ref S68CPH68①
74	Ref F74CPH74①	Ref S74CPH74①

Front Height Inches	Hinge to Box	
	20" W Flush	20" W Surface
	Catalog Number	
26	Ref F26HPH26①	Ref S26HPH26①
32	Ref F32HPH32①	Ref S32HPH32①
38	Ref F38HPH38①	Ref S38HPH38①
44	Ref F44HPH44①	Ref S44HPH44①
50	Ref F50HPH50①	Ref S50HPH50①
56	Ref F56HPH56①	Ref S56HPH56①
62	Ref F62HPH62①	Ref S62HPH62①
68	Ref F68HPH68①	Ref S68HPH68①
74	Ref F74HPH74①	Ref S74HPH74①

Front Height Inches	Door-to-Door	
	20" W Flush	20" W Surface
	Catalog Number	
26	Ref F26DPH26①	Ref S26DPH26①
32	Ref F32DPH32①	Ref S32DPH32①
38	Ref F38DPH38①	Ref S38DPH38①
44	Ref F44DPH44①	Ref S44DPH44①
50	Ref F50DPH50①	Ref S50DPH50①
56	Ref F56DPH56①	Ref S56DPH56①
62	Ref F62DPH62①	Ref S62DPH62①
68	Ref F68DPH68①	Ref S68DPH68①
74	Ref F74DPH74①	Ref S74DPH74①




Figure 4: Screw to Box w/ Piano Hinge Door 1)




Figure 5: Hinge in Box w/ Piano Hinge and Piano Hinge Door




Figure 6: Door in Door w/ Piano Hinge both Doors

① Custom order in COMPAS.

② Stainless 304 is available as a special order for 20" W and 24" W only. Stainless 316 is not available. Flush stainless fronts are typically 1/2" wider and taller than standard flush fronts.