

| Title                                                                                    | Order number       |
|------------------------------------------------------------------------------------------|--------------------|
| <b>October 2018</b>                                                                      |                    |
| <b>SIMATIC WinCC Systemsoftware V7.5 ASIA</b>                                            |                    |
| <b>Runtime package DVD</b>                                                               |                    |
| Language variants: Chinese simpl., Chinese trad., Korean, Japanese, English; license for |                    |
| • WinCC RT Client                                                                        | 6AV6381-2CA07-5AV0 |
| • 128 PowerTags (RT 128)                                                                 | 6AV6381-2BC07-5AV0 |
| • 512 PowerTags (RT 512)                                                                 | 6AV6381-2BD07-5AV0 |
| • 2048 PowerTags (RT 2048)                                                               | 6AV6381-2BE07-5AV0 |
| • 8192 PowerTags (RT 8192)                                                               | 6AV6381-2BH07-5AV0 |
| • 65536 PowerTags (RT 65536)                                                             | 6AV6381-2BF07-5AV0 |
| • 102400 PowerTags (RT 102400)                                                           | 6AV6381-2BJ07-5AV0 |
| • 153600 PowerTags (RT 153600)                                                           | 6AV6381-2BK07-5AV0 |
| • 262144 PowerTags (RT 262144)                                                           | 6AV6381-2BL07-5AV0 |
| incl. respectively 512 archiv variables                                                  |                    |
| <b>RC (Runtime &amp; Configuration) package DVD</b>                                      |                    |
| Language variants: Chinese simpl., Chinese trad., Korean, Japanese, English; license for |                    |
| • WinCC RC Client                                                                        | 6AV6381-2CB07-5AV0 |
| • 128 PowerTags (RC 128)                                                                 | 6AV6381-2BM07-5AV0 |
| • 512 PowerTags (RC 512)                                                                 | 6AV6381-2BN07-5AV0 |
| • 2048 PowerTags (RC 2048)                                                               | 6AV6381-2BP07-5AV0 |
| • 8192 PowerTags (RC 8192)                                                               | 6AV6381-2BS07-5AV0 |
| • 65536 PowerTags (RC 65536)                                                             | 6AV6381-2BQ07-5AV0 |
| • 102400 PowerTags (RC 102400)                                                           | 6AV6381-2BT07-5AV0 |
| • 153600 PowerTags (RC 153600)                                                           | 6AV6381-2BU07-5AV0 |
| • 262144 PowerTags (RC 262144)                                                           | 6AV6381-2BV07-5AV0 |
| incl. respectively 512 archiv variables                                                  |                    |
| <b>SIMATIC WinCC V7.5 Powerpacks</b>                                                     |                    |
| Powerpack packages:                                                                      |                    |
| <b>Runtime package</b>                                                                   |                    |
| • 128 auf 512 PowerTags                                                                  | 6AV6371-2BD07-5AX0 |
| • 512 auf 2048 PowerTags                                                                 | 6AV6371-2BG07-5AX0 |
| • 2048 auf 8192 PowerTags                                                                | 6AV6371-2BM07-5AX0 |
| • 8192 auf 65536 PowerTags                                                               | 6AV6371-2BN07-5AX0 |
| • 65536 auf 102400 PowerTags                                                             | 6AV6371-2BP07-5AX0 |
| • 102400 auf 153600 PowerTags                                                            | 6AV6371-2BQ07-5AX0 |
| • 153600 auf 262144 PowerTags                                                            | 6AV6371-2BR07-5AX0 |
| <b>RC (Runtime &amp; Configuration) package</b>                                          |                    |
| • 128 auf 512 PowerTags                                                                  | 6AV6371-2BD17-5AX0 |
| • 512 auf 2048 PowerTags                                                                 | 6AV6371-2BG17-5AX0 |
| • 2048 auf 8192 PowerTags                                                                | 6AV6371-2BM17-5AX0 |
| • 8192 auf 65536 PowerTags                                                               | 6AV6371-2BN17-5AX0 |
| • 65536 auf 102400 PowerTags                                                             | 6AV6371-2BP17-5AX0 |
| • 102400 auf 153600 PowerTags                                                            | 6AV6371-2BQ17-5AX0 |
| • 153600 auf 262144 PowerTags                                                            | 6AV6371-2BR17-5AX0 |
| <b>SIMATIC WinCC V7.5 Archive</b>                                                        |                    |
| license for:                                                                             |                    |
| • 1500 archive variables (countable)                                                     | 6AV6371-1DQ17-5AX0 |
| • 5000 archive variables (countable)                                                     | 6AV6371-1DQ17-5BX0 |
| • 10000 archive variables (countable)                                                    | 6AV6371-1DQ17-5CX0 |
| • 30000 archive variables (countable)                                                    | 6AV6371-1DQ17-5EX0 |
| <b>SIMATIC WinCC Upgrade</b>                                                             |                    |
| <b>WinCC V7 Upgrade ASIA *1)</b>                                                         |                    |
| • Upgrade RT-Version, V7.2/7.3 -> V7.5                                                   | 6AV6381-2AA07-5AV3 |
| • Upgrade RT-Version, V7.4 -> V7.5                                                       | 6AV6381-2AA07-5AV4 |
| • Upgrade Client RT-Version, V7.2/7.3 -> V7.5                                            | 6AV6381-2CA07-5AV3 |
| • Upgrade Client RT-Version, V7.4 -> V7.5                                                | 6AV6381-2CA07-5AV4 |
| • Upgrade RC-Version, V7.2/7.3 -> V7.5                                                   | 6AV6381-2AB07-5AV3 |

|                                                   |                    |
|---------------------------------------------------|--------------------|
| • Upgrade RC-Version, V7.4 -> V7.5                | 6AV6381-2AB07-5AV4 |
| • Upgrade Client RC-Version, V7.2/7.3 -> V7.5     | 6AV6381-2CB07-5AV3 |
| • Upgrade Client RC-Version, V7.4 -> V7.5         | 6AV6381-2CB07-5AV4 |
| <b>Options for scalable plant configuration</b>   |                    |
| <b>WinCC/Server</b>                               |                    |
| • WinCC V7.5                                      | 6AV6371-1CA07-5AX0 |
| <b>WinCC/WebNavigator V7.5</b>                    |                    |
| • 1 Client License (countable)                    | 6AV6362-1AB00-0BB0 |
| • 3 Client License (countable)                    | 6AV6362-1AD00-0BB0 |
| • 10 Client License (countable)                   | 6AV6362-1AF00-0BB0 |
| • 30 Client License (countable)                   | 6AV6362-1AJ00-0BB0 |
| • 100 Client License (countable)                  | 6AV6362-1AM00-0BB0 |
| <b>WinCC/WebNavigator V7.5 Diagnostics Client</b> |                    |
| • Diagnostics Client                              | 6AV6362-1BA00-0BB0 |
| <b>WinCC/Web Load Balancing V7.5</b>              |                    |
| • Web Load Balancing (2 Licenses)                 | 6AV6362-1FA00-0BB0 |
| • Web Load Balancing StepUp (2 Licenses)          | 6AV6362-1GA00-0BB0 |
| <b>WinCC/WebUX V7.5 Monitor</b>                   |                    |
| • Monitor 1 Client (countable)                    | 6AV6362-2AB00-0BB0 |
| • Monitor 3 Clients (countable)                   | 6AV6362-2AD00-0BB0 |
| • Monitor 10 Clients (countable)                  | 6AV6362-2AF00-0BB0 |
| • Monitor 30 Clients (countable)                  | 6AV6362-2AJ00-0BB0 |
| • Monitor 100 Clients (countable)                 | 6AV6362-2AM00-0BB0 |
| <b>WinCC/WebUX V7.5 Operate</b>                   |                    |
| • Operate 1 Client (countable)                    | 6AV6362-2BB00-0BB0 |
| • Operate 3 Clients (countable)                   | 6AV6362-2BD00-0BB0 |
| • Operate 10 Clients (countable)                  | 6AV6362-2BF00-0BB0 |
| • Operate 30 Clients (countable)                  | 6AV6362-2BJ00-0BB0 |
| • Operate 100 Clients (countable)                 | 6AV6362-2BM00-0BB0 |
| <b>Options for higher availability</b>            |                    |
| <b>WinCC/Redundancy</b>                           |                    |
| • WinCC V7.5                                      | 6AV6371-1CF07-5AX0 |
| <b>Options for IT and Business Integration</b>    |                    |
| <b>WinCC/DataMonitor V7.5</b>                     |                    |
| • 1 Client License (countable)                    | 6AV6362-3AB00-0BB0 |
| • 3 Client License (countable)                    | 6AV6362-3AD00-0BB0 |
| • 10 Client License (countable)                   | 6AV6362-3AF00-0BB0 |
| • 30 Client License (countable)                   | 6AV6362-3AJ00-0BB0 |
| <b>Options for SCADA enhancement</b>              |                    |
| <b>WinCC/User Archives</b>                        |                    |
| • WinCC V7.5                                      | 6AV6371-1CB07-5AX0 |
| <b>Options for individual system enhancement</b>  |                    |
| <b>WinCC/ConnectivityPack V7.5</b>                |                    |
| • WinCC V7.5                                      | 6AV6371-1DR07-5AX0 |
| <b>WinCC/ConnectivityStation V7.5</b>             |                    |
| • WinCC V7.5                                      | 6AV6371-1DR17-5AX0 |
| <b>WinCC/Cloud Connect V7.5</b>                   |                    |
| • WinCC V7.5                                      | 6AV6371-1DR17-5AX0 |
| <b>WinCC V7.5 Upgrade für Basic Optionen</b>      |                    |
| • in WinCC Upgrade included <sup>1)</sup>         |                    |
| <b>WinCC//ODK (Open Development Kit)</b>          |                    |
| • WinCC V7.5                                      | 6AV6371-1CC07-5AX0 |

1) In WinCC Upgrade RT and RC V7.5 Upgrades for basic options are included. Basic options: Datamonitor, Connectivity Pack, Connectivity Station, WebNavigator, User Archives, Server, Redundancy.