

SUPPLIERS DECLARATION OF CONFORMITY for Material Declaration Management

(according to IMO Resolution MEPC.269(68) and EU Ship Recycling Regulation)

- 1) **SDoC ID No.** A5E53571242A, Rev 002
- 2) **Issuers name:** Siemens Aktiengesellschaft, Digital Industries, Process Automation (DI PA)
- Issuers adress:** DE- 76181 Karlsruhe, Germany
- 3) **Object(s) of the declaration:**
- 1) see attachment M- SDoC Declaration
 - 2) _____
 - 3) _____
 - 4) _____
 - 5) _____
 - 6) _____
 - 7) _____
 - 8) _____
 - 9) _____
 - 10) _____

- 4) **The object of declaration described above is in conformity with the requirement of the following documents:**

5) Document No.:	Title:	Edition	Date of
<u>MEPC. Res 269(68)</u>	<u>Guidelines for the Development of Inventory of Hazardous Materials</u>	<u>2015</u>	<u> </u>
<u>SR CONF 45</u>	<u>International Hong Kong Convention for the Safe and Environmentally Sound Recycling of Ships</u>	<u>2009</u>	<u> </u>
<u>ISO 30005</u>	<u>Ships and marine technology — Ship recycling management systems — Information control for hazardous materials in the manufacturing chain of shipbuilding and ship operations</u>	<u>2010</u>	<u> </u>
<u>REGULATION (EU) No 1257/2013</u>	<u>Regulation of the European Parliament and of the Council of 20 November 2013 on ship recycling and amending Regulation (EC) No 1013/2006 and Directive 2009/16/EC</u>	<u>2013</u>	<u> </u>
<u>related to: REGULATION (EU) No 1257/2013</u>	<u>EMSA's Best Practice Guidance on the Inventory of Hazardous Materials</u>	<u>2016</u>	<u> </u>

- 6) **Additional Information:** _____

Signed for and on behalf of:

Siemens Aktiengesellschaft

Karlsruhe
(Place of issue)

07.02.2024
Date of issue

- 7) _____
(Signature)
- _____
(Signature)

Material Declaration

<Date of declaration>

Date	07.02.2024
------	------------

<MD ID Number>

MD- ID-No.	MD ASE53571242A
------------	-----------------

<Supplier (Respondent) Information>

Company Name	Siemens AG
Division Name	DI PA QM&EHS
Address	Östliche Rheinbrückenstraße 50, 76187 Karlsruhe, Germany
Contact Person	Markus Weiler
Telephone Number	+49 1520 9065567
FAX Number	
E-mail Address	markus.weiler@siemens.com
SDOC ID No.:	ASE53571242A, Rev 002

<Other Information>

Remark 1	
Remark 2	
Remark 3	

<Product Information>

Product Name	Product Number	Delivered Unit		Product Information
		amount	Unit	
see attachment	see attachment	1	piece	RoHS compliant; Pb might appear as defined in the exemptions of Annex III and IV of the EU Directive 2011/65/EU

<Material Information>

This material information shows the amount of hazardous materials contained in

unit
1 piece

 (unit: piece,m, m³, litre etc.) of the product.

Table	Material Name		Threshold Level	Present above threshold level	If yes, Material Mass		If yes, Information of Parts/Region of Use
				Yes/No	Mass	Unit	
Table A** (Materials Listed in Appendix 1 of the Convention)	Asbestos		0.1 % *	No			
	Polychlorinated Biphenyls (PCBs)		50 mg/kg	No			
	Ozone Depleting Substance	Chlorofluorocarbons (CFCs)	no threshold level	No			
		Halons		No			
		Other fully halogenated CFCs		No			
		Carbon Tetrachloride		No			
		1,1,1-Trichloroethane		No			
		Hydrochlorofluorocarbons		No			
		Hydrobromofluorocarbons		No			
		Methyl bromide		No			
		Bromochloromethane		No			
	Anti-fouling systems containing organotin compounds as a biocide		2,500 mg/kg	No			

Table	Material Name		Threshold Level	Intentionally added above threshold level	If yes, Material Mass		If yes, Information of Parts/Region of Use
				Yes/No	Mass	Unit	
Table B** (Materials Listed in Appendix 2 of the Convention)	Cadmium and Cadmium Compounds		100 mg/kg	No			
	Hexavalent Chromium and Hexavalent Chromium Compounds		1000 mg/kg	No			
	Lead and Lead Compounds		1000 mg/kg	Yes			PCHM ¹⁾ ; can only be present in exemptions as defined in MEPC 268(68) point 3.3. - "Exemptions – Materials not required to be listed in the Inventory"
	Mercury and Mercury Compounds		1000 mg/kg	No			
	Polybrominated Biphenyl (PBBs)		50 mg/kg	No			
	Polybrominated Diphenyl ethers (PBDEs)		1000 mg/kg	No			
	Polychloronaphthalenes (Cl ≥3)		50 mg/kg	No			
	Radioactive Substances		no threshold level	No			
	Certain Shortchain Chlorinated Paraffins		1%	No			

Annex II*** (Additional Materials)	Perfluorooctane sulfonic acid (PFOS)	10 mg/kg****	No			
	Flame Retardant (HBCDD)	100 mg/kg	No			

*Please refer to footnote 18 on the "Form of Material Declaration" in the IMO Guidelines Resolution MEPC 269(68).

**Hong Kong International Convention for the Safe and Environmentally Sound Recycling of Ships, 2009 (SR/CONF/45).

***Regulation EU No. 1257/2013 of the European Parliament and of the Council of 20 November 2013 on Ship Recycling and amending Regulation EC No. 1013/2006 and Directive 2009/16/EC

EMSA's Best Practice Guidance on the Inventory of Hazardous Materials, dated 2016-10-28

****Concentrations of PFOS above 10 mg/kg (0.001% by weight) when it occurs in substances or in preparations or concentrations of PFOS in semi-finished products or articles, or parts thereof equal to or above than 0.1% by weight calculated reference to the mass of structurally or micro-structurally distinct parts that contain PFOS or for textiles or other coated materials, if the amount of PFOS is equal to or above than 1 µg/m² of the coated material

¹⁾ Potentially Containing Hazardous Material

Scalance X-M

6GK5004-1XXX-XXXX	6GK5408-0XXX-XXXX
6GK5004-2XXX-XXXX	6GK5408-4XXX-XXXX
6GK5005-0XXX-XXXX	6GK5408-8XXX-XXXX
6GK5008-0XXX-XXXX	6GK5416-4XXX-XXXX
6GK5102-1XXX-XXXX	6GK5423-4XXX-XXXX
6GK5104-0XXX-XXXX	6GK5424-8XXX-XXXX
6GK5106-2XXX-XXXX	6GK5428-8XXX-XXXX
6GK5108-0XXX-XXXX	6GK5432-0XXX-XXXX
6GK5108-2XXX-XXXX	6GK5524-8XXX-XXXX
6GK5112-0XXX-XXXX	6GK5526-8XXX-XXXX
6GK5116-0XXX-XXXX	6GK5528-0XXX-XXXX
6GK5124-0XXX-XXXX	6GK5532-2XXX-XXXX
6GK5200-4XXX-XXXX	6GK5534-2XXX-XXXX
6GK5201-3XXX-XXXX	6GK5534-3XXX-XXXX
6GK5202-2XXX-XXXX	6GK5552-0XXX-XXXX
6GK5204-0XXX-XXXX	6GK5615-0XXX-XXXX
6GK5204-2XXX-XXXX	6GK5622-2XXX-XXXX
6GK5205-3XXX-XXXX	6GK5626-2XXX-XXXX
6GK5206-1XXX-XXXX	6GK5632-2XXX-XXXX
6GK5206-2XXX-XXXX	6GK5636-2XXX-XXXX
6GK5208-0XXX-XXXX	6GK5642-2XXX-XXXX
6GK5212-2XXX-XXXX	6GK5646-2XXX-XXXX
6GK5213-3XXX-XXXX	6GK5791-2XXX-XXXX
6GK5216-0XXX-XXXX	6GK5812-1XXX-XXXX
6GK5216-3XXX-XXXX	6GK5816-1XXX-XXXX
6GK5216-4XXX-XXXX	6GK5826-1XXX-XXXX
6GK5224-0XXX-XXXX	6GK5991-1XXX-XXXX
6GK5224-4XXX-XXXX	6GK5991-2XXX-XXXX
6GK5307-3XXX-XXXX	6GK5991-4XXX-XXXX
6GK5308-2XXX-XXXX	6GK5992-1XXX-XXXX
6GK5310-0XXX-XXXX	6GK5992-2XXX-XXXX
6GK5320-0XXX-XXXX	6GK5992-4XXX-XXXX
6GK5320-3XXX-XXXX	6GK5998-3XXX-XXXX
6GK5323-4XXX-XXXX	6GK7177-1XXX-XXXX
6GK5324-0XXX-XXXX	6GK7543-1XXX-XXXX
6GK5324-4XXX-XXXX	
6GK5324-8XXX-XXXX	
6GK5328-4XXX-XXXX	
6GK5332-0XXX-XXXX	
6GK5334-2XXX-XXXX	
6GK5334-3XXX-XXXX	
6GK5400-8XXX-XXXX	

Scalance W-M-WLAN

6GK5786-1XXX-XXXX
6GK5721-1XXX-XXXX
6GK5722-1XXX-XXXX
6GK5734-1XXX-XXXX
6GK5738-1XXX-XXXX
6GK5748-1XXX-XXXX
6GK5761-1XXX-XXXX
6GK5763-1XXX-XXXX
6GK5766-1XXX-XXXX
6GK5774-1XXX-XXXX
6GK5778-1XXX-XXXX
6GK5786-1XXX-XXXX
6GK5786-2XXX-XXXX
6GK5788-1XXX-XXXX
6GK5788-2XXX-XXXX

SFP Transceiver

6GK5991-1XXX-XXXX
6GK5992-1XXX-XXXX
6GK5993-1XXX-XXXX

NET Relais

6GK1503-2XXX
6GK1503-3XXX
6GK1503-4XXX
6NH3112-0XXX-XXXX
6NH3112-3XXX-XXXX
6NH3112-4XXX-XXXX
6ES7440-1XXX-XXXX

SPG-PLC

6DL4163-1XXX-XXXX
6DL4163-5XXX-XXXX
6ES7972-0XXX-XXXX
6GK1411-1XXXX
6GK1411-5XXXX
6GK1500-0XXXX
6GK1500-3XXXX
6GK1571-1XXXX
6GK7242-5XXXX-XXXX
6GK7243-1XXXX-XXXX
6GK7243-5XXXX-XXXX
6GK7243-8XXXX-XXXX
6GK7277-1XXXX-XXXX
6GK7342-5XXXX-XXXX
6GK7343-1XXXX-XXXX
6GK7343-5XXXX-XXXX
6GK7377-1XXXX-XXXX
6GK7442-1XXXX-XXXX
6GK7443-1XXXX-XXXX
6GK7443-5XXXX-XXXX
6GK7542-1XXXX-XXXX
6GK7542-5XXXX-XXXX
6GK7542-6XXXX-XXXX
6GK7543-1XXXX-XXXX
6GK7543-6XXXX-XXXX
6GK7545-1XXXX-XXXX
6NH3112-3XXXX-XXXX
6NH7800-3XXXX
6NH7800-4XXXX
6NH7803-3XXXX-XXXX
6NH7803-4XXXX-XXXX

SPG-IID

6GT2002-0LA00