

Measured Components of PN-Rea V2.0 (ID7)

Component		Type	MLFB	Version
IO controller	S7-300	CPU 315-2DP	6ES7 315-2AG10-0AB0	V 2.0
		CP 343-1	6GK7 343-1EX21-0XE0	V 1.1
		CPU 315-2 PN/DP	6ES7 315-2EG10-0AB0	V 2.3
		CPU 317-2PN/DP	6ES7 317-2EJ10-0AB0	V 2.3
		CPU 319-3PN/DP	6ES7 318-3EL00-0AB0	V 2.4
	S7-400	CPU 414-2DP	6ES7 414-2XG04-0AB0	V 4.0
		CP 443-1 Adv.	6GK7 443-1EX40-0XE0	V 2.4
		CPU 416-2DP	6ES7 416-2XK04-0AB0	V 4.0
	Network topology	switch	SCALANCE X108	6GK5 108-0BA00-2AA3
Access Point		AP W 786-1RR	6GK5 788-1SR00-2AA3	V 2.4
Client module		CM W 747-1RR	6GK5 747-1SR00-2AA6	V 2.4
ET200S PN		IM151-3	6ES7 151-3AA20-0AB0	
		I/O module (4 DI)	6ES7 131-4BD01-0AA0	
		I/O module (4 DO)	6ES7 132-4BD01-0AA0	
Network load	PG	PC with STEP 7	6ES7 710..	
STEP 7		V5.3 SP3 HF1		