


Supplementary components

Displays

SITRANS RD300

Overview



The SITRANS RD300 is a panel mount remote digital display for process instrumentation and acts as a multi-purpose, easy to use, rate/totalizer ideal for flow rate, total, and control applications.

Benefits

- Easy setup and programming via front panel buttons or using free RD software available via USB drive
- Display readable in sunlight
- Input: accepts current and voltage
- Single or dual 24 V DC transmitter power supply
- Serial communication using built in protocol or Modbus RTU
- Supports up to 8 relays and 8 digital I/O for process control and alarming
- 32-Point linearization, square root or exponential linearization
- Multi-pump alternation control
- Supports total, grand total or non-resettable grand total
- 9-digit totalizer with total overflow feature
- Large dual-line, 6-digit display
- Configure, monitor, and datalog from a PC
- Dual-input option with math functions: addition, difference, average, multiplication, division, minimum, maximum, weighted average, ratio, concentration

Application

The RD300 is a remote display for level, flow, pressure, weighing, and other process instruments. This display also acts as a multi-purpose, easy to use rate/totalizer ideal for flow rate, total, and control applications.

Data can be remotely collected, logged and presented on your local computer using the free RD software available via USB drive.

The display accepts a single or dual input of current and voltage. This makes the RD300 an ideal fit for use with most field instruments.

The RD300 can be set up as a standard panel mount, or combined with optional enclosures to allow it to house up to 6 displays.

- Key Applications: tank farms, pump alternation control, local or remote display of level, flow, pressure and weighing instrument values, PC monitoring and data logging with RD Software.

Selection and ordering data

SITRANS RD300 Display		Article No.									
Remote digital panel mount process display with current or voltage inputs. Two input, multi-line display, totalizer and pump control.		7ML5744-	●	●	●	●	●	-	0	A	
Click on the Article No. for the online configuration in the PIA Life Cycle Portal.											
Input voltage											
85 ... 265 V AC, 50/60 Hz; 90 ... 265 V DC, 20 W max.				1							
12 ... 36 V DC; 12 ... 24 V AC, 6 W max.				2							
Output											
None					A						
2 Relays					B						
4 Relays					C						
4 ... 20 mA output					D						
2 Relays and 4 ... 20 mA output					E						
4 Relays and 4 ... 20 mA output					F						
Type											
Single input process and flow rate/totalizer Mtr					A						
Dual input process Mtr					B						
Display											
Standard								0			
SunBright								1			
Approvals											
UL, cUL, and CE									0		

Selection and Ordering data	Article No.
Operating Instructions	
All literature is available to download for free, in a range of languages, at http://www.siemens.com/processinstrumentation/documentation	
Accessories	
DIN-Rail Mounting Kit	7ML1930-6AB
4 Relays Expansion Module	7ML1930-6AC
4 Digital I/O Module	7ML1930-6AD
Dual output 4 ... 20 mA expansion module for dual input meter	7ML1930-6AP
Meter Copy Cable	7ML1930-6AE
RD300 RS 232 Serial Adapter	7ML1930-6AF
RD300 RS 422/485 Serial Adapter	7ML1930-6AG
RD300 USB Serial Adapter	7ML1930-6AJ
USB to RS 232 Converter	7ML1930-6AK
RS 232 to RS 422/485 isolated converter	7ML1930-1BU
RS 232 to RS 422/485 non-isolated converter	7ML1930-1BV
USB to RS 422/485 isolated converter	7ML1930-1BX
USB to RS 422/485 non-isolated converter	7ML1930-1BY
Snubber	7ML1930-6AL
Plastic enclosure	
For 1 meter	7ML1930-6AM
For 2 meters	7ML1930-6AN
For 4 meters	7ML1930-1CK
For 5 meters	7ML1930-1CL
For 6 meters	7ML1930-1CM

Supplementary components

Displays

SITRANS RD300


Technical specifications

SITRANS RD300	
Mode of operation	
Measuring principle	Analog to digital conversion
Measuring points	1 or 2 instruments
Input	
Measuring range	
• Current	4 ... 20 mA, 0 ... 20 mA
• Voltage	0 V DC ... +10 V DC, 1 ... 5 V, 0 ... 5 V
Output signal	
Output	4 ... 20 mA (optional) - Modbus RTU
Relays	2 or 4 SPDT (Form C) internal and/or 4 SPST (Form A) external; rated 3 A at 30 V DC and 125/250 V AC resistive load; 1/14 HP (50 W) at 125/250 V AC for inductive loads (optional)
Communications	- RS 232 with Modbus RTU - RS 422/485 with Modbus RTU - USB configuration and monitoring port
Accuracy	
4 ... 20 mA optional output	± 0.1 % FS ± 0.004 mA
Process input	± 0.05 % of span ± 1 count, square root: 10 ... 100 % FS
Rated operating conditions	
Ambient conditions	
• Storage temperature range	-40 ... +85 °C (-40 ... +185 °F)
• Operating temperature range	-40 ... +65 °C (-40 ... +149 °F)
Design	
Weight	269 g (9.5 oz) (including options)
Material (enclosure)	1/8 DIN, high impact plastic, UL94V-0, color: gray - Optional plastic, steel and stainless steel (Type 304, EN 1.4301) NEMA 4 enclosures
Degree of protection	Type 4X, NEMA 4X, IP65 (front cover); panel gasket provided
Electrical connection	
mA output signal	2-core copper conductor, twisted, shielded, 0.82 ... 3.30 mm ² (18 ... 12 AWG), Belden 8 760 or equivalent is acceptable
Electrical connection and relay connection	Copper conductor according to local requirements, rated 3 A at 250 V AC
Power supply	
Input voltage option	85 ... 265 V AC, 50/60 Hz; 90 ... 265 V DC, 20 W max. or jumper selectable 12/24 V DC ± 10 %, 15 W max.
Transmitter power supply	Terminals P+ & P-: 24 V DC ± 10 %, 12/24 V DC powered models selectable for 24, 10, or 5 V DC supply (internal jumper J4), 85 ... 265 V AC models rated at 200 mA max, 12/24 V DC powered models rated at 100 mA max., at 50 mA max. for 5 or 10 V DC supply.
External loop power supply	35 V DC max.
Output loop resistance	24 V DC, 10 ... 700 Ω max. 35 V DC (external), 100 ... 1 200 Ω max.
Displays and controls	
Main display	0.6 inch (15 mm) high, red LEDs
Second display	0.46 inch (12 mm) high, red LEDs, 6-digits: each (-99 999 ... 999 999)
Memory	- Non-volatile - Stores settings for minimum of 10 years if power is lost
Programming	- Primary: front panel - Secondary: Meter Copy or PC with SITRANS RD Software
Certificates and approvals	
CE, UL, cUL	

Technical specifications (continued)

SITRANS RD300	
Options	
Enclosures	Plastic, steel and stainless steel (Type 304, EN 1.4301) NEMA 4 and 4X enclosures

Dimensional drawings



SITRANS RD300, dimensions in mm (inch)


Supplementary components

Displays


SITRANS RD300

Circuit diagrams


Connector labeling for fully loaded single input meter




Transmitter powered by external supply or self-powered



Transmitter powered by internal supply



Voltage Input Connections



SITRANS RD300 connections