

Certificate of Compliance

Certificate: 214695

Project: 1290399

Date Issued: February 14, 2002

Issued To: Siemens AG
A&D CD CP TS2
Werner-von-Siemens-Strasse 48
Amberg, 92220
Germany
Att: Mr. Rolf Mueller

The products listed below are eligible to bear the CSA Mark shown



Issued by:


Nancy Graham

Authorized by:


Nick Alfano
Operations Manager

PRODUCTS

3211 03 INDUSTRIAL CONTROL EQUIPMENT Motor Controllers - Auxiliary Devices

Type 3UG3082-1AW30, 3UG3081-1AK20, 3UG3081-1AW30, supply voltage 24V ac, 42-48V ac, 110-130V ac, 220-240V ac, 24-240V ac/dc, 380-415V ac, 480-500V ac, 600V ac, measuring voltage, 50-MV-600V ac, control circuit 5A, 250V ac, B300.

MARKINGS

The CSA Mark, the company name, and/or tradename/ or identification/ or file number 214695, model designation, and any 'Cautions' or other information as specified in the Certification Report.



CSA INTERNATIONAL

Supplement to Certificate of Compliance

Certificate: 214695

*The products listed, including the latest revision described below,
are eligible to be marked in accordance with the referenced Certificate.*

Product Certification History

<u>Revision</u>	<u>Date</u>	<u>Submittor</u>	<u>Description</u>	<u>Listee</u>
LR 12684 1290399	February 14, 2002	<u>Entrelec-Schiele</u>	IWN-DC IWN-AC 115/240 IWN-24-240V	<u>Siemens AG</u> 3LLG3082-1AW30 3UG3081-1AK20 3UG3081-1AW30



CSA INTERNATIONAL

CERTIFICATION RECORD

The company named below has been authorized by CSA to represent the products listed in this record as "CSA Certified" and to affix the CSA Mark to these products according to the terms and conditions of the CSA Service Agreement and applicable CSA program requirements (including additional Markings).

Alternate File: 214695

Class No: 3211 03 INDUSTRIAL CONTROL EQUIPMENT Motor Controllers - Auxiliary Devices

LISTEE

4543559 Siemens AG
A&D CD CP TS2
Werner-von-Siemens-Strasse 48
Amberg, 92220
Germany

February 14, 2002

- Type 3UG3082-1AW30, 3UG3081-1AK20, 3UG3081-1AW30, supply voltage 24V ac, 42-48V ac, 110-130V ac, 220-240V ac, 24-240V ac/dc, 380-415V ac, 480-500V ac, 600V ac, measuring voltage, 50-MV-600V ac, control circuit 5A, 250V ac, B300.

/ey