## Load Cells

Compression load cells SIWAREX WL270 CP-S SB

## Load cell

## Overview



The compression load cell is particularly suitable for implementation in container, hopper and vehicle scales.

### Design

The measuring element is a solid cylinder made of stainless steel to which 4 strain gauges are applied.

The load which acts centrally in the measuring direction causes the spring bodies and therefore the friction-locked strain gauges to be elastically deformed. This generates a measuring signal voltage that is proportional to the load.

# Technical specifications

SIWAREX WL270 CP-S SB				
Possible applications	Hopper scales			
Type of construction	Can compression cell			
Rated load/maximum load Emax.	100 t			
Accuracy class according to OIML R-60	C3			
Max. scale interval n <sub>LC</sub>	3 000			
Min. scale interval $V_{min}$ • $E_{max} = 100 \text{ t}$	E <sub>max</sub> /9 000			
Minimum application range $R_{\min(LC)}$	33%			
Combined error $F_{\text{comb}}$	± 0.02% C <sub>n</sub>			
Repeatability $F_v$	± 0.02% C <sub>n</sub>			
Creep error F <sub>cr</sub> • 30 min	± 0.023% C <sub>n</sub>			
Temperature coefficient • Zero signal <i>T</i> <sub>Ko</sub> • Characteristic value <i>T</i> <sub>Kc</sub>	0.023% <i>C</i> n/5 K 0.017% <i>C</i> n/5 K			
Min. dead load E <sub>min</sub>	0 kg			
Max. working load L <sub>u</sub>	150% E <sub>max</sub>			
Breaking load L <sub>D</sub>	300% <i>E</i> <sub>max</sub>			
Safe side load L <sub>lq</sub>	10% <i>E</i> <sub>max</sub>			
Deflection $h_{n}$ at $E_{max}$	0.36 mm			
Recommended supply voltage (range)	5 12 V DC			
Rated characteristic value $C_n$	$2.0 \pm 0.02 \text{ mV/V}$			
Tolerance $D_0$ of zero signal	$\leq \pm 1.0\% C_n$			
Input resistance R <sub>e</sub>	$700 \ \Omega \pm 7 \ \Omega$			
Output resistance R <sub>a</sub>	$700 \Omega \pm 7 \Omega$			
Insulation resistance $R_{\rm is}$	5 000 MΩ at 50 V DC			
Rated temperature range $B_{tn}$	-10 +40 °C (14 104 °F)			
Operating temperature range $B_{tu}$	-35 +65 °C (-31 149 °F)			
Storage temperature range $B_{ts}$	-35 +65 °C (-31 149 °F)			
Sensor material	Stainless steel EN 1.4542			
Degree of protection according to EN 60529; IEC 60529	IP68			
Cable connection				
Function • EXC + (supply +) • EXC - (supply -) • SIG + (measured signal +) • SIG - (measured signal -) • Sense + (sensor cable +)	Color Green Black White Red Yellow			
<ul> <li>Sense – (sensor cable -)</li> <li>Shield (not connected to the load)</li> </ul>	Blue			

Shield (not connected to the load Transparent cell body)

## Selection and ordering data

Load cell, type WL270 CP-S SB		7MH5710-			
Legal-for-trade according to OIML R-60 up to 3 000d, 20 m connecting cable	-		D	0	
Click on the Article No. for the online configuration in the PIA Life Cycle Portal.					
Rated load					
• 100 t (98.42 tn. l.)	6	A			
Explosion protection					
Without					0
• Explosion protection for zones 0, 1, 2, 20, 21, 22					1

# Load Cells

Compression load cells SIWAREX WL270 CP-S SB

Load cell

Dimensional drawings



SIWAREX WL 270 CP-S SB load cell, dimensions in mm (inch)

3

## Load Cells Compression load cells SIWAREX WL270 CP-S SB

## Mounting unit

## Overview



The self-centering mounting unit for SIWAREX WL270 CP-S SA load cells is particularly suitable for implementation in container scales.

## Desian

The mounting unit comprises a base plate and a top plate, two pressure pieces, two clamping pieces and two centering sleeves. There are threaded holes in the base plate and top plate for the subsequent flange-fitting of guide elements.

The top plate is aligned and fixed above the base plate with the two centering sleeves. This results in a stable unit. The height of the top plate is adjusted so that it is five millimeters above the installation height with load cell.

Two pressure pieces are used to mount the load cell. They are fastened flush with the head plate and base plate using the clamping pieces.

In this state, the mounting unit serves as an installation aid and can be used as a dummy for light installation jobs.

Prior to installation, the load cell is inserted into the mounting unit. Then the complete unit is installed in the scales. As a result, the load bearing implement and the mounting units are aligned. The load cells are not yet loaded.

Finally, the load bearing implement is lowered by loosening the two hexagon nuts under the centering sleeves. The weight now rests on the load cells.

In this state the load cell and the pressure pieces together form a self-centering unit. The mounting unit permits sideways displacement of the top plate, and hence of the load bearing implement, by up to eight millimeters in all directions. Two countersunk screws prevent the load bearing implement from being lifted off or toppling off.

Using the mounting unit as an installation aid results in optimum alignment of the load cells. This is essential to enable the load cells to perform at their best in terms of accuracy.

For maintenance or troubleshooting purposes, the load cell can be relieved again by tightening the hexagon nuts. Replacement of the load cell is then easy after the clamping pieces are released.

#### Technical specifications

Mounting unit for load cells of the SIWAREX WL270 CP-S SB series				
Rated load	100 t (98.42 tn. l)			
Maximum lateral deflection with load cell	± 8 mm (0.12 inch)			
Lifting path of the top plate	3 5 mm (0.12 0.20 inch)			
Restoring force per millimeter of lateral deflection of the top plate in % of the applied load with load cell	0.5%/mm			
Permissible supporting load with fixed top plate	140 kN			

Permissible lifting force on the 140 kN top plate Permissible lateral force on the 50 kN top plate with fixed top plate

#### Selection and ordering data

#### Mounting unit

• 100 t (98.42 tn. l.)

For load cells of the SIWAREX WL270 CP-S SB series Material: Stainless steel EN 1.4301 and EN 1.4112 For load cells with a rated load of 1)2)

#### 7MH5710-6AA00

Article No.

1) The load cell is not included in the scope of delivery.

<sup>2)</sup> It is highly recommendable to use a grounding cable (7MH3701-1AA1) in order to protect the load cell.

#### Dimensional drawings



Mounting unit for SIWAREX WL270 CP-S SB load cells (installation state), dimensions in mm (inch)

#### Pressure piece set

Article No.

7MH5710-6AD00

## Overview



In combination with a pressure piece set, the SIWAREX WL270 CP-S SA load cell produces a self-centering self-aligning bearing. This unit is particularly suitable for installation in container, hopper and vehicle scales.

## Design

The pressure piece set consists of an upper and lower pressure piece. Together with the load cell the pressure piece set forms a self-centering unit with integrated torsion guard.

The self-centering, self-aligning bearing thus formed allows the load bearing element to follow horizontal displacements (e.g. due to temperature fluctuations) In this case the construction of the self-aligning bearing creates a restoring force which is dependent on the size of the displacement and the applied load.

If the load bearing implement is displaced by more than 8 mm (0.32 inch) in the horizontal direction, measures for restricting sideways play (e.g. in the form of endstops or guide elements) must be provided in the construction of the load bearing implement. Lifting of the load support must be prevented by suitable measures provided in the construction of the load bearing implement.

The load cell must be ordered separately.

## Technical specifications

Pressure piece set for the individual installation of load cells of the type SIWAREX WL270 CP-S SB				
Rated load	100 t (98.42 tn. l)			
Maximum lateral deflection with load cell	± 8 mm (0.12 inch)			
Restoring force per millimeter of lateral deflection of the top plate in % of the applied load with load cell	0.5%/mm			

#### Selection and ordering data

#### Pressure piece sets<sup>1)</sup>

For the individual installation of load cells from the SIWAREX WL270 CP-S SB series

Material: Stainless steel EN 1.4112 For load cells with a rated load of  $^{(1)2)}$ 

- 100 t (98.42 tn. l.)
- <sup>1)</sup> The principles of general mechanical engineering and safety must be
- observed.
   <sup>2)</sup> It is highly recommendable to use a grounding cable (7MH3701-1AA1) in order to protect the load cell.
- <sup>3)</sup> The load cell is not included in the scope of delivery.

## Dimensional drawings



Pressure piece for SIWAREX WL270 CP-S SB load cells, dimensions in mm (inch)