

Electronic Mini Circuit Breakers

eQP Circuit Breaker

1 - 2-pole; 10A - 60A



1-Pole Combination
Type AFCI



2-Pole Combination
Type AFCI



1-Pole Dual
Function AFCI/GFCI



1-Pole AFCI
Plug-on Neutral



1-Pole Dual Function
Plug-on Neutral



1-Pole GFCI



2-Pole GFCI



1-Pole Equipment
Protection



2-Pole Equipment
Protection

Combination Type AFCI

Amperage	Poles	QAF2 (10kAIC)	QAFH2 (22kAIC)	HQAF2 (65kAIC)	QAF2N (10kAIC)
15	1	QA115AFC	QA115AFCH	QA115AFCHH	QA115AFCN
20	1	QA120AFC	QA120AFCH	QA120AFCHH	QA120AFCN
Amperage	Poles	QAF (10kAIC)	QAFH (22kAIC)	–	QAFN (10kAIC)
15	2	Q215AFC	Q215AFCH	–	Q215AFCN
20	2	Q220AFC	Q220AFCH	–	Q220AFCN

Dual Function AFCI/GFCI

Amperage	Poles	QFGA2 (10kAIC)	QFGAH2 (22kAIC)	HQFGA2 (65kAIC)	QFGA2N (10kAIC)
15	1	Q115DF	Q115DFH	Q115DFHH	Q115DFN
20	1	Q120DF	Q120DFH	Q120DFHH	Q120DFN

Ground-Fault Circuit Interrupters (GFCI) (5mA)

Amperage	Poles	QPF2 (10kAIC)	QPHF2 (22kAIC)	HQPF2 (65kAIC)	QPF2N (10kAIC)
15	1	QF115A	QF115AH	QF115AHH	QF115AN
20	1	QF120A	QF120AH	QF120AHH	QF120AN
30	1	QF130A	QF130AH	QF130AHH	QF130AN
15	2	QF215A	QF215AH	–	–
20	2	QF220A	QF220AH	–	–
30	2	QF230A	QF230AH	–	–
40	2	QF240A	QF240AH	–	–
50	2	QF250A	QF250AH	–	–
60	2	QF260A	QF260AH	–	–

Ground-Fault Circuit Interrupters (GFCI) (30mA)

Amperage	Poles	QE (10kAIC)	QEH (22kAIC)
15	1	QE115	QF115AH
20	1	QE120	QE120H
30	1	QE130	QE130H
15	2	QE215	QE215H
20	2	QE220	QE220H
30	2	QE230	QE230H
40	2	QE240	QE240H
50	2	QE250	QE250H
60	2	QE260	QE260H

External Accessories

Description	Catalog Number	No. of Poles
Padlocking Device	ECPLD1	1
	ECPLD1R	1
	ECPLD2	2
	ECPLD2R	2
Handle Blocking Device	ECQX231M	1

Standards:

AFCI Circuit Breakers

UL 489 and UL 943

CSA C22.2 NO. 270

Class A GFCI Circuit Breakers (5mA)

UL 489 and UL 943

CSA C22.2 No. 144.1

NMX-J-520-ANCE

Equipment GFCI Circuit Breakers

UL 489 and 1053

CSA C22.2 No. 144

Dual Function Devices (AFCI/GFCI)

UL 489, UL 1699 and UL 943

CSA C22.2 No. 144.1-06 and 5-16

Pressure Wire Connectors

Load Side terminal factory installed only

Breaker Type	Ampere Rating	Cables per Lug	No. of Poles	Wire Range
QAF, QAFH, HQAF, QFGA, QFGAH, HQFGA, QLF, QLFH, QLE & QLEH	15 - 20	1	1, 2, 3	#14 - #10 AWG Cu
		1	1, 2, 3	#12 - #10 AWG Al.
	25 - 35	1	1, 2, 3	#10 - #8 AWG Cu.
		1	1, 2, 3	#10 - #6 AWG Al.
	40 - 50	1	1, 2, 3	#8 - #6 AWG Cu.
		1	1, 2, 3	#8 - #4 AWG Al.
	55 - 60	1	1, 2	#6 - #4 AWG Cu.
		1	1, 2	#6 - #4 AWG Al.

Published by Siemens 2020

Siemens Industry, Inc.
3617 Parkway Ln.
Peachtree Corners, GA 30092

Siemens Technical Support: 1-800-333-7421
info.us@siemens.com

Printed in USA-CP
Order No. RPFL-EQPCB-0920
All Rights Reserved
© 2020, Siemens Industry, Inc.
usa.siemens.com/resibreakers

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.