

Ordering
overview

Edition
11/2023

SIMATIC NET

Cabling technology for communication networks in industry

based on Industrial Ethernet/PROFINET and PROFIBUS

[siemens.com/fastconnect](https://www.siemens.com/fastconnect)

Cabling technology for communication networks in industry

A faultless on-site connection in 60 seconds with FastConnect

Problems often occur on-site when laying the cabling for industrial plants: when stripping the cable, assembling the plug-in connector, or connecting the cores.

The FastConnect (FC) quick assembly system from Siemens is the right system for:

- Optimally matched components for configuration of industry standard and robust network structures within the shortest possible time and without specialist knowledge
- Minimal amount of time for connecting terminal devices
- Avoidance of installation errors
- Simple on-site assembly
- Reduction of overall costs throughout the entire system lifetime

FastConnect includes cables, connectors and tools, and can be used for Industrial Ethernet, PROFINET, EtherNet/IP as well as for PROFIBUS.

With its optimally matched components, SIMATIC NET cables enable the installation of high-performance industrial network structures.

- Minimal installation time
- Easy stripping of outer sheath and braided shield in one step
- Simple connection system for Industrial Ethernet FastConnect cables
- Easy assembly thanks to preset FastConnect stripping tool

- Reliable shield contacting and strain relief
- M12 and RJ45 connection system for Industrial Ethernet, PROFINET, EtherNet/IP and PROFIBUS

Your benefits with FastConnect

With the FastConnect (FC) system for Industrial Ethernet, structured cabling from the office environment becomes industry-compliant:



- Coordinated system of FC plug-in connectors and an extensive FC cable spectrum for a wide variety of requirements in the industrial sector and energy automation
- UL approvals for Industrial Ethernet, PROFINET, EtherNet/IP, and PROFIBUS enable worldwide use
- Avoidance of errors thanks to color coding, preset tools, and defined materials
- Reliable shield contacting and strain relief as well as efficient EMC shielding for copper cabling
- Use of standard-compliant connection systems for Industrial Ethernet, PROFINET, EtherNet/IP, and PROFIBUS
- Fulfills environmental requirements in accordance with IEC 61850-3 and EN 45545 fire protection standard in rail vehicles



FastConnect for Industrial Ethernet/PROFINET

Quick connection of FastConnect (FC) RJ45 plug-in connectors 2 × 2 and 4 × 2

The Industrial Ethernet RJ45 plug-in connector for easy on-site assembly of 4- and 8-wire twisted pair FC installation cables (up to 10 Gbps) using the Industrial Ethernet stripping tool



Prefabricated with RJ45-plug-in connector 2 × 2

Cabling system FastConnect RJ45

<https://youtu.be/XQjVYFMR8Mk>

Cabling technology for communication networks in industry


FastConnect for Industrial Ethernet/PROFINET: Prefabricated with RJ45 plug-in connector 4 × 2




Measure the cable end




Cut the cable end with the FastConnect stripping tool




Remove the outer sheath and expose the braided shield




Remove the interior support cross



Unravel and smooth out the twisted wires




Insert the wires into the plug according to color code and pull them out the opposite side



Press the plug casing to close it



Fasten the casing using a screwdriver



Remove protruding wires

Assembling videos


IE FastConnect Cat7 cable with RJ45 plug on-site assembly
youtu.be/m3cnXbnkpn4

FastConnect Cabling System M12 Gigabit
youtu.be/CSwDQptulds

FO Cabling System FastConnect
youtu.be/o2COYEzdvX8

FastConnect (FC) M12 plug-in connector 2 × 2 and 4 × 2

Industrial Ethernet M12 plug-in connector for easy on-site assembly with degree of protection IP65/67 for connecting 4- and 8-wire twisted pair FC installation cables (up to 10 Gbps) using the Industrial Ethernet stripping tool






Prefabricated with M12 plug-in connector 2 × 2



Prefabricated with M12 plug-in connector 4 × 2

FastConnect (FC) LC and ST/BFOC plug-in connector

The Industrial Ethernet FastConnect LC and ST/BFOC plug-in connectors for easy on-site assembly of FastConnect glass fiber optic cables (62.5/200/230 μm multimode fibers) for lengths up to 3 km (100/1000 Mbps Industrial Ethernet/PROFIBUS) using the FastConnect FO termination kit



Prefabricated FastConnect for glass fiber optic cables

Cabling technology for communication networks in industry

FastConnect for PROFIBUS

Fast connection of FastConnect (FC) sub-D plug-in connectors

The PROFIBUS (FC) sub-D plug-in connector for easy on-site assembly of 2-wire FC installation cables (up to 12 Mbps) using the PROFIBUS stripping tool



Stripping and assembly using insulation displacement system

FastConnect (FC) M12 plug-in connector






















The PROFIBUS (FC) M12 plug-in connector for easy on-site assembly of 2-wire FC installation cables (up to 12 Mbps) using the PROFIBUS stripping tool












Stripping and assembly with M12 plug-in connector














Cabling technology for communication networks in industry

Overview






		Electrical	Industrial Ethernet (IE) cables											
		Connection options with connectors, terminals or devices (IE)												
		IE FC cable 4 x 2	IE FC cable 2 x 2	IE TP cord 2 x 2	IE TP cord 4 x 2	IE connecting cable RJ45	IE connecting cable M12	Power cable						
														
IE FC standard cable GP 4 x 2 (AWG22)	IE FC standard cable GP 4 x 2 (AWG24) IE FC flexible cable GP 4 x 2 (AWG24) IE FC trailing cable GP 4 x 2 (AWG24) IE FC ground cable 4 x 2 (AWG24)	IE train cable GP 4 x 2 (AWG24)	IE FC TP cable GP 2 x 2	IE TP cord 9-45/RJ45	IE TP cord RJ45/RJ45 IE TP XP cord RJ45/RJ45	IE FC RJ45 PLUG-180/ IE FC RJ45 PLUG-180	M12-180IM12-180 M12-180IE FC RF45 PLUG-145, M12-90IM12-90	Power cable 2 x 0.75	Power cable 5 x 1.5	Energy Cable 4 x 1.5	Robust power cable 4 x 0.75	Control Cable 5 x 0.25		
	IE FC RJ45 modular outlet	●				●								
	IE FC outlet RJ45			●	●	●								
	IE FC RJ45 plug 2 x 2			●										
	IE FC RJ45 plug 4 x 2		●											
	IE FC Keystone RJ45		●											
	M12 power and data connector	A-coded						●					●	
		L-coded								●				
		2 x 2 D-coded			●									
		4 x 2 X-coded	●	●										
	Devices with M12 connection													
	Devices with RJ45 port				●	●								
	Power plug PRO								●					
	Power M12 plug PRO													
	Power M12 cable connector PRO													
	7/8 inch plug-in connector								●					
	IE FC RJ45 plug PRO			●										
	Power Plug M12 S-kodiert													




Electrical Industrial Ethernet (IE) cables				
	Product	Comments	Article number ¹⁾	
Industrial Ethernet FastConnect cables 2 × 2 with 10/100 Mbps				
	IE FC TP Standard Cable GP (Type A)	Standard bus cable 2 × 2, for permanent installation, rigid cores for fast assembly, sold by the meter, max. delivery unit 2 000 m, minimum order quantity 20 m	6XV1840-2AH10	
		TP installation cable for connecting to FC outlet RJ45, for universal use, Cat5e	20 m	6XV1840-2AN20
			50 m	6XV1840-2AN50
			100 m	6XV1840-2AT10
			200 m	6XV1840-2AT20
500 m	6XV1840-2AT50			
1 000 m	6XV1840-2AU10			
	IE FC TP Robust Standard Cable GP (Type A)	Robust standard bus cable 2 × 2, for harsh industrial environments, Cat5e, sold by the meter, max. delivery unit 2 000 m, minimum order quantity 20 m	6XV1841-2A	
	IE FC TP Flexible Cable GP (Type B)	Flexible bus cable 2 × 2, for occasionally moved machine parts, Cat5e, sold by the meter, max. delivery unit 2 000 m, minimum order quantity 20 m	6XV1870-2B	
		Flexible bus cable 2 × 2, for occasionally moved machine parts, Cat5e, delivery unit 1 000 m	1 000 m 6XV1870-2BU10	
	IE FC Robust Flexible Cable GP (Type B)	Robust, flexible bus cable 2 × 2, for harsh industrial environments, Cat5e, sold by the meter, max. delivery unit 2 000 m, minimum order quantity 20 m	6XV1841-2B	
	IE FC TP FRNC Cable GP (Type B)	Flexible, halogen-free bus cable 2 × 2, for occasionally moved machine parts, Cat5e, sold by the meter, max. delivery unit 2 000 m, minimum order quantity 20 m	6XV1871-2F	
			1 000 m 6XV1871-2FU10	
		IE TP Torsion Cable (Type C)	Torsion cable (PROFINET type C) 2 × 2, for use in highly flexible applications (torsion), Cat5e, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1870-2F
IE TP Robot Cable 2 × 2 (Type R)		TP installation cable, 4-core, for use in highly flexible robot applications (torsion, drag chains), sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1840-2R	
			6XV1840-3AH10	
	IE FC TP Trailing Cable (Type C)	TP installation cable for cable carrier applications, 4-core, shielded Cat5e, sold by the meter (4 million bending cycles), max. delivery unit 2 000 m, minimum order quantity 20 m	6XV1840-3AH10	
	IE FC TP Trailing Cable GP (Type C)	Highly flexible bus cable 2 × 2, continuous motion control in a cable carrier, Cat5e, sold by the meter, max. delivery unit 2 000 m, minimum order quantity 20 m	6XV1870-2D	
			0.3 m	6XV1870-8AE30
			0.5 m	6XV1870-8AE50
			1.0 m	6XV1870-8AH10
			1.5 m	6XV1870-8AH15
			2.0 m	6XV1870-8AH20
			3.0 m	6XV1870-8AH30
			5.0 m	6XV1870-8AH50
			10 m	6XV1870-8AN10
			15 m	6XV1870-8AN15
			20 m	6XV1870-8AN20
			30 m	6XV1870-8AN30
40 m	6XV1870-8AN40			
50 m	6XV1870-8AN50			
	IE Connecting Cable M12-180/M12-180 (D-coded)	Prefabricated flexible connecting cable 2 × 2 with two 4-pin M12 connectors (D-coded), for connecting Industrial Ethernet devices (e.g., SIMATIC ET 200pro, SCALANCE X208PRO, SCALANCE XP-200) in degree of protection IP65/IP67, preferred length	0.3 m	6XV1870-8AE30
			0.5 m	6XV1870-8AE50
			1.0 m	6XV1870-8AH10
			1.5 m	6XV1870-8AH15
			2.0 m	6XV1870-8AH20
			3.0 m	6XV1870-8AH30
			5.0 m	6XV1870-8AH50
			10 m	6XV1870-8AN10
15 m	6XV1870-8AN15			
20 m	6XV1870-8AN20			
30 m	6XV1870-8AN30			
40 m	6XV1870-8AN40			
50 m	6XV1870-8AN50			
	IE Connecting Cable M12-90/M12-90 (D-coded)	Prefabricated connecting cable 2 × 2, with two M12 connectors (D-coded), 90° cable outlet	0.3 m	6XV1870-8GE30
			0.5 m	6XV1870-8GE50
			1.0 m	6XV1870-8GH10
			1.5 m	6XV1870-8GH15
			2.0 m	6XV1870-8GH20
			3.0 m	6XV1870-8GH30
			5.0 m	6XV1870-8GH50
			10 m	6XV1870-8GN10
15 m	6XV1870-8GN15			
	IE Connecting Cable M12-180/M12-180 (D-coded, Push Pull)	Prefabricated with IE FC Trailing Cable GP, M12 connectors (D-coded, push pull, for ET200S Busadapter)	0.5 m	6XV1871-8AE50
			1.0 m	6XV1871-8AH10
			1.5 m	6XV1871-8AH15
			2.0 m	6XV1871-8AH20
			3.0 m	6XV1871-8AH30
			5.0 m	6XV1871-8AH50
			10.0 m	6XV1871-8AN10
15.0 m	6XV1871-8AN15			
	Unlocking straps for M12 BA	Unlocking straps 10 units, for push pull M12 plug, for BusAdapter with M12 socket	10 units 6ES7193-6DL00-2AA0	
	IE Connecting Cable M12-180/IE FC RJ45 Plug 145 (D-coded)	Prefabricated flexible connecting cable 2 × 2, with one 4-pin M12 connector (D-coded) and one IE FC RJ45 plug 145, for connecting Industrial Ethernet devices (e.g., SIMATIC ET 200pro, SCALANCE X208PRO, SCALANCE XP-200 and SIMOTION), preferred length	2.0 m	6XV1871-5TH20
3.0 m			6XV1871-5TH30	
5.0 m			6XV1871-5TH50	
10 m			6XV1871-5TN10	
15 m			6XV1871-5TN15	










Electrical Industrial Ethernet (IE) cables				
	Product	Comments		Article number ¹⁾
Industrial Ethernet FastConnect cables 2 × 2 with 10/100 Mbps (continued)				
	IE Connecting Cable M12-90/ IE FC RJ45 Plug-180 (D-coded)	Prefabricated IE FC TP trailing cable GP 2 × 2 (PROFINET type C) with M12 connector (D-coded, 90° cable outlet) and with IE FC RJ45 plug 180	5.0 m	6XV1871-5MH50
		Prefabricated IE FC TP trailing cable GP 2 × 2 (PROFINET type C) with two IE FC RJ45 plugs 180, degree of protection IP20	1.0 m	6XV1871-5BH10
			2.0 m	6XV1871-5BH20
			3.0 m	6XV1871-5BH30
			5.0 m	6XV1871-5BH50
			10 m	6XV1871-5BN10
			12 m	6XV1871-5BN12
			15 m	6XV1871-5BN15
			20 m	6XV1871-5BN20
30 m	6XV1871-5BN30			
	IE FC TP Robust Food Cable GP (Type C)	TP installation cable 2 × 2 for use in the food, beverages and tobacco industry, IP69, Cat5e, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m		6XV1881-2A
	IE Robust Connecting Cable M12, IP69 (D-coded)	Prefabricated IE robust connecting cable 2 × 2 M12-180/M12-180, IP69, with two M12 connectors (D-coded)	1.0 m	6XV1881-5AH10
			2.0 m	6XV1881-5AH20
			3.0 m	6XV1881-5AH30
			5.0 m	6XV1881-5AH50
	IE FC TP Food Cable (Type C)	Flexible bus cable 2 × 2 for use in the food, beverages and tobacco industry, Cat5e, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m		6XV1871-2L
	IE FC TP Marine Cable (Type B)	Bus cable 2 × 2 for marine and offshore use, Cat5e, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m		6XV1840-4AH10
	IE FC TP Festoon Cable GP (Type B)	Bus cable 2 × 2 for festoon mounting, Cat5e, sold by the meter (min. 5 million bending cycles), max. delivery unit 1 000 m, minimum order quantity 20 m		6XV1871-2S
	IE TP Ground Cable (Type C)	Bus cable 2 × 2 for permanent installation in the ground, Cat5e, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m		6XV1871-2G
	IE Robust Ground Cable (Type C)	IE robust ground cable 2 × 2, underground laying cable, 4-core shielded with rodent protection, Cat5e, sold by the meter, delivery unit max. 1 000 m, minimum order 20 m		6XV1871-2N
	IE TP Train Cable GP (Type C)	Bus cable 2 × 2 for special applications in trains, certified for railway applications, Cat5e, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m		6XV1871-2T
Industrial Ethernet FastConnect cables 4 × 2 for 1 Gbps and 10 Gbps				
	IE FC TP Standard Cable GP	Standard bus cable 4 × 2, AWG22, standard cable with rigid cores for fast assembly, for permanent installation, Cat6A, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m		6XV1870-2E
	IE FC TP Standard Cable GP 4 × 2, Cat7	Cat6A, TP installation cable, 8-core, for use in highly flexible applications (torsion), sold by the meter, delivery unit max. 1 000 m, minimum order quantity 20 m		6XV1876-2A
	IE FC TP Flexible Cable GP 4 × 2, Cat7	TP installation cable Cat7 for connection to IE FC RJ45 plug, AWG26/7, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m		6XV1876-2B
	IE FC TP Standard Cable GP (Type C)	Standard bus cable 4 × 2, AWG24, standard cable with rigid cores for fast assembly, for permanent installation, Cat6A, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m		6XV1878-2A
			1 000 m	6XV1878-2AU10
	IE FC TP Flexible Cable GP (Type C)	Bus cable 4 × 2, AWG24/7, with flexible cores, flexible cable for fast installation, for occasionally moved machine parts, Cat6A, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m		6XV1878-2B
	IE FC TP FRNC Cable GP (Type C)	Flexible TP cable for occasional movement for connection to FC RJ45 plug 4 × 2, 8-core, shielded, Cat6A, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m		6XV1878-2F
	IE TP Train Cable GP (Type C)	Bus cable 4 × 2, AWG24/7, with flexible cores, for use in trains, certified for railway applications, Cat7, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m		6XV1878-2T
	IE FC TP Torsion Cable 4x2 (Type C)	Cat6A, TP installation cable, 8-core, for use in highly flexible applications (torison), sold by the meter, delivery unit max. 1 000 m, minimum order quantity 20 m		6XV1878-2D
	IE FC TP Trailing Cable GP (Type C)	FastConnect TP trailing cable GP 4 × 2, TP installation cable Cat6A, for connecting to IE FC RJ45 plug 4 × 2, AWG24, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m		6XV1878-2C

Electrical Industrial Ethernet (IE) cables				
	Product	Comments	Article number ¹⁾	
	IE Connecting Cable RJ45-180/RJ45-180	Prefabricated IE FC flexible cable GP 4 × 2, with two IE FC RJ45 plugs 180 4 × 2	2.0 m	6XV1878-5BH20
			3.0 m	6XV1878-5BH30
			5.0 m	6XV1878-5BH50
			10 m	6XV1878-5BN10
			15 m	6XV1878-5BN15
			20 m	6XV1878-5BN20
			25 m	6XV1878-5BN25
			30 m	6XV1878-5BN30
	IE FC TP Ground Cable (Type C)	Ground extension cable 4 × 2, shielded cable for connecting to IE FC RJ45 plug 4 × 2, AWG24, Cat6A, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1878-2G	
IE hybrid cable				
	IE Hybrid Cable	Ethernet hybrid cable 2 × 2 + 4 × 0.34, for transmission of data and power, Cat5, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1870-2J	
Power cables				
	Control Cable ET200ecoPN 5 × 0.25	5-core power line, stranded wire, 5 × AWG24, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1801-2C	
	Power Cable 2 × 0.75	Power cable for connection of signaling contact and 24 V power supply to SCALANCE X and SCALANCE W, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1812-8A	
	Power Cable 5 × 1.5	Power cable, power supply for ET 200 modules, with 7/8 power interface, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1830-8AH10	
	Robust Power Cable 4 × 0.75	Robust power cable, for use in the food, beverages and tobacco industry, IP69, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1801-2A	
	Robust Energy Cable 4 × 1.5	Robust energy cable for use in the food and beverage industry, IP69, sold by the meter, delivery unit max. 1 000 m, minimum order quantity 20 m	6XV1801-2E	
	Energy Cable 4 × 1.5	4-core power line, stranded wire, 4 × 1.5 mm ² , trailable, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1801-2B	
	FRNC Energy Cable 4 × 1.5	4-core, halogen-free power line, stranded wire 4 × 1.5 mm ² , sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1801-2F	
	M12 Robust Power Connecting Cable M12-180/M12-180 (A-coded)	Prefabricated robust power plug-in cable, IP69, for power supply of the ET 200, with M12 connector and M12 socket (A-coded, 4 × 0.75 mm ²)	1.0 m	6XV1801-5AH10
			2.0 m	6XV1801-5AH20
			3.0 m	6XV1801-5AH30
			5.0 m	6XV1801-5AH50
	M12 Power Connecting Cable M12-180/M12-1802) (A-coded)	Prefabricated flexible plug-in cable, with one 4-pin M12 male/female connector (A-coded, 4 × 0.75 mm ²), plug-in cable for connecting the 24 V power supply to ET 200eco PN in degree of protection IP65/67, preferred length	0.3 m	6XV1801-5DE30
			0.5 m	6XV1801-5DE50
			1.0 m	6XV1801-5DH10
			1.5 m	6XV1801-5DH15
			2.0 m	6XV1801-5DH20
			3.0 m	6XV1801-5DH30
			5.0 m	6XV1801-5DH50
	M12 Power Connecting Cable M12-90/M12-90 (A-coded)	Prefabricated power plug-in cable 2 × 2, for power supply of the ET 200, with M12 connector and M12 socket (A-coded, 4 × 0.75 mm ²)	10 m	6XV1801-5DN10
			15 m	6XV1801-5DN15
			0.3 m	6XV1801-5GE30
			0.5 m	6XV1801-5GE50
			1.0 m	6XV1801-5GH10
			1.5 m	6XV1801-5GH15
			2.0 m	6XV1801-5GH20
			3.0 m	6XV1801-5GH30
5.0 m	6XV1801-5GH50			
10 m	6XV1801-5GN10			
15 m	6XV1801-5GN15			

Electrical Industrial Ethernet (IE) cables				
	Product	Comments		Article number ¹⁾
Power cables (continued)				
	7/8" Plug-in Cable	Prefabricated 7/8" power plug-in cable, for power supply of the ET 200 with 7/8" connector and 7/8" socket	0.3 m	6XV1822-5BE30
			0.5 m	6XV1822-5BE50
			1.0 m	6XV1822-5BH10
			1.5 m	6XV1822-5BH15
			2.0 m	6XV1822-5BH20
			3.0 m	6XV1822-5BH30
			5.0 m	6XV1822-5BH50
			10 m	6XV1822-5BN10
			15 m	6XV1822-5BN15
	Power Connecting Cable M12-180/M12-180 (L-coded)	Power supply, harness cable with M12 connector and M12 socket (L-coded, 4 × 1.5 mm ²)	0.5 m	6XV1801-6DE50
			1.0 m	6XV1801-6DH10
			1.5 m	6XV1801-6DH15
			2.0 m	6XV1801-6DH20
			3.0 m	6XV1801-6DH30
			5.0 m	6XV1801-6DH50
			10 m	6XV1801-6DN10
	Power Connecting Cable M12-90/M12-90 (L-coded)	Power supply of the ET200, harness cable with M12 connector and M12 socket (L-coded, 4 × 1.5 mm ²)	0.5 m	6XV1801-6GE50
			1.0 m	6XV1801-6GH10
			1.5 m	6XV1801-6GH15
			2.0 m	6XV1801-6GH20
			3.0 m	6XV1801-6GH30
			5.0 m	6XV1801-6GH50
			10 m	6XV1801-6GN10
	Control Connecting Cable M12-180/M12-180 (A-coded)	5-core, IO link port class B, prefabricated with M12 connector and M12 socket (A-coded, 5 × 0.25 mm ²), straight cable duct	0.5 m	6XV1801-2CE50
			1.0 m	6XV1801-2CH10
			1.5 m	6XV1801-2CH15
			2.0 m	6XV1801-2CH20
			3.0 m	6XV1801-2CH30
			5.0 m	6XV1801-2CH50
			10 m	6XV1801-2CN10
15 m	6XV1801-2CN15			
IE TP cord – Easy connection of terminal devices to the IE FC cabling system				
	IE TP Cord RJ45/RJ45	Prefabricated 8-wire Cat6A patch cable 4 × 2, with two RJ45 connectors, preferred length	0.3 m	6XV1870-3QE30
			0.5 m	6XV1870-3QE50
			1.0 m	6XV1870-3QH10
			2.0 m	6XV1870-3QH20
			3.0 m	6XV1870-3QH30
			4.0 m	6XV1870-3QH40
			6.0 m	6XV1870-3QH60
			10 m	6XV1870-3QN10
			15 m	6XV1870-3QN15
			20 m	6XV1870-3QN20
			25 m	6XV1870-3QN25
			30 m	6XV1870-3QN30
			35 m	6XV1870-3QN35
			40 m	6XV1870-3QN40
			45 m	6XV1870-3QN45
			50 m	6XV1870-3QN50



Electrical Industrial Ethernet (IE) cables				
	Product	Comments		Article number ¹⁾
IE TP cord – Easy connection of terminal devices to the IE FC cabling system (continued)				
	IE TP Cord RJ45/RJ45	Pre-assembled 8-core Cat6A patch cable 4 × 2, with two RJ45-plugs, standard length (red)	0.5 m	6XV 1870-4RE50
			1.0 m	6XV 1870-4RH10
			2.0 m	6XV 1870-4RH20
			3.0 m	6XV 1870-4RH30
			4.0 m	6XV 1870-4RH40
			6.0 m	6XV 1870-4RH60
			10 m	6XV 1870-4RN10
			15 m	6XV 1870-4RN15
			20 m	6XV 1870-4RN20
			25 m	6XV 1870-4RN25
	IE TP Cord RJ45/RJ45	Pre-assembled 8-core Cat6A patch cable 4 × 2, with two RJ45-plugs, standard length (blue)	0.5 m	6XV1870-4BE50
			1.0 m	6XV1870-4BH10
			2.0 m	6XV1870-4BH20
			3.0 m	6XV1870-4BH30
			4.0 m	6XV1870-4BH40
			6.0 m	6XV1870-4BH60
			10 m	6XV1870-4BN10
			15 m	6XV1870-4BN15
			20 m	6XV1870-4BN20
			25 m	6XV1870-4BN25
	IE TP Cord RJ45/RJ45	Pre-assembled 8-core Cat6A patch cable 4 × 2, with two RJ45-plugs, standard length (grey)	0.5 m	6XV1870-4UE50
			1.0 m	6XV1870-4UH10
			2.0 m	6XV1870-4UH20
			3.0 m	6XV1870-4UH30
			4.0 m	6XV1870-4UH40
			6.0 m	6XV1870-4UH60
			10 m	6XV1870-4UN10
			15 m	6XV1870-4UN15
			20 m	6XV1870-4UN20
			25 m	6XV1870-4UN25
	IE TP Cord RJ45	Pre-assembled 8-core Cat6A patch cable 4 × 2, with two RJ45-plugs, standard length (yellow)	0.5 m	6XV1870-4GE50
			1.0 m	6XV1870-4GH10
			2.0 m	6XV1870-4GH20
			3.0 m	6XV1870-4GH30
			4.0 m	6XV1870-4GH40
			6.0 m	6XV1870-4GH60
			10 m	6XV1870-4GN10
			15 m	6XV1870-4GN15
			20 m	6XV1870-4GN20
			25 m	6XV1870-4GN25
	IE TP Cord M12-180/RJ45-180 (X-coded)	Prefabricated IE Flexible Cable, with 1 × M12 connector (X-coded), 180° cable outlet and 1 × RJ45 connector, 180° cable outlet	0.5 m	6XV1878-5TE50
			1.0 m	6XV1878-5TH10
			1.5 m	6XV1878-5TH15
			2.0 m	6XV1878-5TH20
			3.0 m	6XV1878-5TH30
			5.0 m	6XV1878-5TH50
			10 m	6XV1878-5TN10
			15 m	6XV1878-5TN15
			30 m	6XV1878-5TN30
			50 m	6XV1878-5TN50





Electrical Industrial Ethernet (IE) cables				
	Product	Comments		Article number ¹⁾
IE TP cord – Easy connection of terminal devices to the IE FC cabling system (continued)				
	IE TP Cord M12-90/RJ45-180 (X-coded)	Prefabricated IE Flexible Cable with 1 × M12 connector (X-coded), 90° cable outlet and 1 × RJ45 connector, 180° cable outlet	0.5 m	6XV1878-5SE50
			1.0 m	6XV1878-5SH10
			1.5 m	6XV1878-5SH15
			2.0 m	6XV1878-5SH20
			3.0 m	6XV1878-5SH30
			5.0 m	6XV1878-5SH50
			10 m	6XV1878-5SN10
	IE TP XP Cord RJ45/RJ45	Prefabricated twisted 8-wire Cat6A patch cable 4 × 2, with two RJ45 connectors, preferred length	0.5 m	6XV1870-3RE50
			1.0 m	6XV1870-3RH10
			2.0 m	6XV1870-3RH20
			6.0 m	6XV1870-3RH60
	IE TP Cord M12/M12 (X-coded)	Prefabricated flexible Cat6A cable 4 × 2, with two M12 connectors (X-coded)	10 m	6XV1870-3RN10
			0.3 m	6XV1878-5HE30
			0.5 m	6XV1878-5HE50
			1.0 m	6XV1878-5HH10
			1.5 m	6XV1878-5HH15
			2.0 m	6XV1878-5HH20
			3.0 m	6XV1878-5HH30
			5.0 m	6XV1878-5HH50
			10 m	6XV1878-5HN10
			15 m	6XV1878-5HN15
			30 m	6XV1878-5HN30
	IE TP Cord M12-90/M12-90 (X-coded)	Prefabricated Cat6A IE flexible cable, with two M12 connectors (X-coded), 90° cable outlet	50 m	6XV1878-5HN50
			80 m	6XV1878-5HN80
			0.5 m	6XV1878-5GE50
			1.0 m	6XV1878-5GH10
			1.5 m	6XV1878-5GH15
			2.0 m	6XV1878-5GH20
			3.0 m	6XV1878-5GH30
5.0 m	6XV1878-5GH50			
10 m	6XV1878-5GN10			
15 m	6XV1878-5GN15			




		Optical	Industrial Ethernet (IE) cables										
		Connection options with connectors, terminals or devices											
		Fiber optic cables 50/125/1 400 µm	Fiber optic cables 62.5/125 µm	PCF fiber optic cables 200/230 µm	Fiber optic cables with ST/BFOC connector	Fiber optic cables with SC connector	Fiber optic cables with LC connector	POF fiber optic cables 980/1 000 µm	Fiber optic cable with SC RJ connector	Fiber optic cables for LC connector	Fiber optic cables with FC connector		
		FO standard cable GP FO trailing cable FO trailing cable GP FO ground cable	Fiber optic standard cable INDOOR fiber optic cable Flexible fiber optic trailing cable SIENOPYR marine duplex fiber optic cable	PCF standard cable GP PCF trailing cable GP PCF trailing cable	Prefabricated fiber optic cables with ST/BFOC connector	Prefabricated fiber optic cables with SC connector	Prefabricated fiber optic cables with LC connector	POF standard cable GP POF trailing cable	Prefabricated fiber optic cables with SC RJ connector	FO FRNC Cable GP (2E9/125/900) FO Robust Cable GP (4E9/125/900)	FO Standard Cable GP (50/125/900) FO FRNC Cable GP (50/125/900) FO Flexible Cable GP (50/125/900) FO Robust Cable GP (50/125/900)	FO FC Standard Cable GP (62.5/200/230)	FO FC Trailing Cable (62.5/200/230)
	ST/BFOC connector	•	•		•								
	IE devices with ST/BFOC connection				•								
	SC connector	•	•										
	SC connector						•			•	•		
	IE devices with SC connection					•							
	IE Devices with LC connection						•						
	SC RJ connector			•				•					
	IE Devices with SC RJ connection							•					
	IE SC RJ POF plug PRO							•					
	IE SC RJ PCF plug PRO			•									
	Multimode FO LC plug										•		
	FO FC ST/BFOC plug											•	•
	FO FC LC plug											•	•









G_IKT0_XX_10246





Note:
See page 17 for our portfolio of prefabricated fiber optic cords (adapter cables) with a range of connection options

Optical Industrial Ethernet (IE) cables				
	Product	Comments	Article number ¹⁾	
FC glass fiber optic cables				
	FC FO Standard Cable GP 62.5/200/230 (OM1)	Glass fiber optic cable for assembly in the field, for use at permanent location, installation in cable channels and pipes, UL approval, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1847-2A	
	FC FO Trailing Cable 62.5/200/230 (OM1)	Flexible glass fiber optic cable for assembly in the field, for high mechanical loads, for use in cable carriers indoors and outdoors, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1847-2C	
Glass fiber optic cables				
	FO Standard Cable GP 50/125/1400 (OM2++, Type C)	Glass fiber optic cable for use indoors and outdoors, UL approval, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1873-2A	
			0.5 m	6XV1873-3AH05
			1.0 m	6XV1873-3AH10
			2.0 m	6XV1873-3AH20
			3.0 m	6XV1873-3AH30
			5.0 m	6XV1873-3AH50
			10 m	6XV1873-3AN10
			15 m	6XV1873-3AN15
			20 m	6XV1873-3AN20
			30 m	6XV1873-3AN30
			40 m	6XV1873-3AN40
			50 m	6XV1873-3AN50
			80 m	6XV1873-3AN80
			100 m	6XV1873-3AT10
			150 m	6XV1873-3AT15
		200 m	6XV1873-3AT20	
		300 m	6XV1873-3AT30	
		Prefabricated with 2 × 2 ST/BFOC connectors	1.0 m	6XV1873-5AH10
			2.0 m	6XV1873-5AH20
			3.0 m	6XV1873-5AH30
			5.0 m	6XV1873-5AH50
			10 m	6XV1873-5AN10
			15 m	6XV1873-5AN15
			20 m	6XV1873-5AN20
			30 m	6XV1873-5AN30
			40 m	6XV1873-5AN40
			50 m	6XV1873-5AN50
			80 m	6XV1873-5AN80
			100 m	6XV1873-5AT10
			150 m	6XV1873-5AT15
			200 m	6XV1873-5AT20
			300 m	6XV1873-5AT30
		Prefabricated with 2 × LC duplex connectors	0.5 m	6XV1873-6AH05
			1.0 m	6XV1873-6AH10
			2.0 m	6XV1873-6AH20
			3.0 m	6XV1873-6AH30
5.0 m	6XV1873-6AH50			
10 m	6XV1873-6AN10			
15 m	6XV1873-6AN15			
20 m	6XV1873-6AN20			
30 m	6XV1873-6AN30			
40 m	6XV1873-6AN40			
50 m	6XV1873-6AN50			
80 m	6XV1873-6AN80			
100 m	6XV1873-6AT10			
150 m	6XV1873-6AT15			
200 m	6XV1873-6AT20			
300 m	6XV1873-6AT30			
Prefabricated with 2 × SC duplex connectors	0.5 m	6XV1873-6AH05		
	1.0 m	6XV1873-6AH10		
	2.0 m	6XV1873-6AH20		
	3.0 m	6XV1873-6AH30		
	5.0 m	6XV1873-6AH50		
	10 m	6XV1873-6AN10		
	15 m	6XV1873-6AN15		
	20 m	6XV1873-6AN20		
	30 m	6XV1873-6AN30		
	40 m	6XV1873-6AN40		
	50 m	6XV1873-6AN50		
	80 m	6XV1873-6AN80		
	100 m	6XV1873-6AT10		
	150 m	6XV1873-6AT15		
	200 m	6XV1873-6AT20		
300 m	6XV1873-6AT30			



Optical Industrial Ethernet (IE) cables				
	Product	Comments	Article number ¹⁾	
Glass fiber optic cables (continued)				
	FO FRNC Cable 50/125/1400 (OM2++, Type B)	Glass fiber optic cable, halogen-free cable for use indoors and outdoors, for permanent installation, UL approval, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1873-2B	
	FO FRNC Cable 50/125/900 (OM4, Type B)	Glass fiber optic cable, halogen-free cable for use indoors and outdoors, for permanent installation, UL approval, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1873-2E	
	FO Connecting Cable LC/MM 50/125/900 (OM4, Type B)	Fiber-optic cable, halogen-free, pre-assembled at bilaterally with 2 × LC-Duplex connector for installation with MRB85536M, standard length	50 m 6XV1883-4FN50	
	FO FLEXIBLE Cable 50/125/900 (OM4, Type C)	Glass fiber optic cable, halogen-free cable, divisible, for permanent installation, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1873-2F	
		Glass fiber optic cable, flexible cable for use in cable carriers with high mechanical load, no UL approval, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1873-2C	
		Prefabricated with 2 × 2 ST/BFOC connectors	3.0 m	6XV1873-3CH30
			5.0 m	6XV1873-3CH50
			10 m	6XV1873-3CN10
			20 m	6XV1873-3CN20
			50 m	6XV1873-3CN50
			100 m	6XV1873-3CT10
	FO Trailing Cable 50/125/1400 (OM2++, Type C)	Prefabricated with 2 × LC duplex connectors	5.0 m	6XV1873-5CH50
			10 m	6XV1873-5CN10
			15 m	6XV1873-5CN15
			20 m	6XV1873-5CN20
		Prefabricated with 2 × SC duplex connectors	3.0 m	6XV1873-6CH30
			5.0 m	6XV1873-6CH50
			10 m	6XV1873-6CN10
			20 m	6XV1873-6CN20
			50 m	6XV1873-6CN50
		100 m	6XV1873-6CT10	
		Trailing cable, segmentable, without connector, UL approval, sold by the meter, max. unit of delivery 1 000 m, minimum order quantity 20 m	6XV1873-2D	
	FO Trailing Cable GP 50/125/1400 (OM2++, Type C)	Prefabricated with 2 × 2 ST/BFOC connectors, preferred length	3.0 m	6XV1873-3DH30
			5.0 m	6XV1873-3DH50
			10 m	6XV1873-3DN10
			20 m	6XV1873-3DN20
			50 m	6XV1873-3DN50
		100 m	6XV1873-3DT10	
	FO Trailing Cable GP 50/125/1400 (OM2++, Type C)	Prefabricated with 2 × SC duplex connectors, preferred length	3.0 m	6XV1873-6DH30
			5.0 m	6XV1873-6DH50
			10 m	6XV1873-6DN10
			20 m	6XV1873-6DN20
			50 m	6XV1873-6DN50
		100 m	6XV1873-6DT10	
		Glass fiber optic cable, waterproof lengthwise and sideways with non-metallic protection against rodents, for use outdoors as well as for direct installation in the ground, sold by the meter, max. delivery unit 2 000 m, minimum order quantity 20 m	6XV1873-2G	
	FO Ground Cable 50/125/1400 (OM2++, Type C)	Prefabricated with 2 × 2 ST/BFOC connectors, preferred length	100 m	6XV1873-3GT10
			200 m	6XV1873-3GT20
			300 m	6XV1873-3GT30
		Prefabricated with 2 × SC duplex connectors, preferred length	100 m	6XV1873-6GT10
			200 m	6XV1873-6GT20
			300 m	6XV1873-6GT30

Optical Industrial Ethernet (IE) cables				
	Product	Comments	Article number ¹⁾	
Glass fiber optic cables (continued)				
	FO Robust Cable GP 50/125/900 (OM2+, Type C)	Glass fiber optic cable, waterproof lengthwise and sideways with non-metallic protection against rodents, for use indoors and outdoors as well as for direct installation in the ground, multimode, sold by the meter Prefabricated with 2 x LC duplex connectors	1.0 m	6XV1873-5RH10
			2.0 m	6XV1873-5RH20
			3.0 m	6XV1873-5RH30
			10 m	6XV1873-5RN10
			30 m	6XV1873-5RN30
			50 m	6XV1873-5RN50
			100 m	6XV1873-5RT10
			150 m	6XV1873-5RT15
	SM FO FRNC Cable GP 2E9/125/900	Fiber-optic cable, halogen-free, splittable, for permanent routing, max. length 1 000 m minimum, order quantity 20 m sold by the meter	6XV1843-2E	
	FO Connecting Cable LC/SM 9/125/900 (OS1, Type B)	Fiber-optic cable, halogen-free, pre-assembled at bilaterally with 2 x LC-Duplex plug for installation with MRB85536M, standard length	50 m 6XV1883-4FN50	
	FO Robust Cable GP 4E9/125/900	Glass fiber optic cable, waterproof lengthwise and sideways with non-metallic protection against rodents, for use indoors and outdoors as well as for direct installation in the ground, singlemode, sold by the meter	6XV1843-2R	
	FO Standard Cable 62.5/125/900 (OM1)	Fiber optic flexible cable, for use indoors and outdoors, sold by the meter, max. delivery unit 2 000 m, minimum order quantity 20 m Prefabricated with 2 x 2 ST/BFOC connectors, preferred length	1.0 m	6XV1820-5AH10
			2.0 m	6XV1820-5BH10
			3.0 m	6XV1820-5BH20
			4.0 m	6XV1820-5BH30
			5.0 m	6XV1820-5BH40
			10 m	6XV1820-5BH50
			15 m	6XV1820-5BN10
			20 m	6XV1820-5BN15
			30 m	6XV1820-5BN20
			40 m	6XV1820-5BN30
			50 m	6XV1820-5BN40
			55 m	6XV1820-5BN50
			60 m	6XV1820-5BN55
			65 m	6XV1820-5BN60
			70 m	6XV1820-5BN65
			75 m	6XV1820-5BN70
			80 m	6XV1820-5BN75
			100 m	6XV1820-5BN80
			120 m	6XV1820-5BN85
			130 m	6XV1820-5BN90
150 m	6XV1820-5BT10			
200 m	6XV1820-5BT15			
250 m	6XV1820-5BT20			
300 m	6XV1820-5BT25			
	Fiber Optic Indoor Cable 62.5/125/900, segmentable (OM1)	Glass fiber optic cable, crush-proof, halogen-free and flame-retardant cable for indoor installation, sold by the meter, max. delivery unit 2 000 m, minimum order quantity 20 m Prefabricated with 2 x 2 ST/BFOC connectors, preferred length	0.5 m	6XV1820-7AH10
			1.0 m	6XV1820-7BH05
			2.0 m	6XV1820-7BH10
			3.0 m	6XV1820-7BH20
			5.0 m	6XV1820-7BH30
			10 m	6XV1820-7BH50
			15 m	6XV1820-7BN10
			20 m	6XV1820-7BN15
			25 m	6XV1820-7BN20
			25 m	6XV1820-7BN25
			50 m	6XV1820-7BN50
			75 m	6XV1820-7BN75
100 m	6XV1820-7BN100			






Optical Industrial Ethernet (IE) cables				
	Product	Comments	Article number ¹⁾	
Glass fiber optic cables (continued)				
	Fiber Optic Flexible Cable 62.5/125/1400, segmentable (OM1)	Flexible glass fiber optic cable, for use in cable carriers indoors and outdoors, sold by the meter, max. delivery unit 2 000 m, minimum order quantity 20 m	6XV1820-6AH10	
		Prefabricated with 2 × 2 ST/BFOC connectors, preferred length	1.0 m	6XV1820-6BH10
			2.0 m	6XV1820-6BH20
			3.0 m	6XV1820-6BH30
			5.0 m	6XV1820-6BH50
			10 m	6XV1820-6BN10
			15 m	6XV1820-6BN15
			20 m	6XV1820-6BN20
			30 m	6XV1820-6BN30
			50 m	6XV1820-6BN50
75 m	6XV1820-6BN75			
100 m	6XV1820-6BT10			
	Fiber Optic Multimode Cord	Prefabricated multimode glass fiber optic cable, SC/SC, 50/125, with 2 × SC duplex connectors	1.0 m 6XV1843-5EH10-0CCO	
		Prefabricated multimode glass fiber optic cable, SC/ST/BFOC, 50/125, with 1 × SC duplex connector and 2 × ST/BFOC connectors	1.0 m 6XV1843-5EH10-0CB0	
		Prefabricated multimode glass fiber optic cable, SC/LC, 50/125, with 1 × SC duplex connector and 1 × LC duplex connector	1.0 m 6XV1843-5EH10-0CA0	
		Prefabricated multimode glass fiber optic cable, ST/BFOC/LC, 50/125, with 2 × ST/BFOC connectors and 1 × LC duplex connector	1.0 m 6XV1843-5EH10-0AB0	
		Prefabricated multimode glass fiber optic cable, LC/LC, 50/125, with 2 × LC duplex connectors	1.0 m 6XV1843-5EH10-0AA0	
		Multimode fiber-optic cord LC/LC; 50/125; pre-assembled with 2 × LC full duplex connectors; length 2.0 m	2.0 m 6XV1843-5EH20-0AA0	
		Pre-assembled multimode fiber-optic cord LC/LC; 50/125; pre-assembled with 2 × LC full duplex connectors	3.0 m 6XV1843-5EH30-0AA0	
Fiber Optic Singlemode Cord	Prefabricated singlemode glass fiber optic cable, SC/SC, 9/125, with 2 × SC duplex connectors	1.0 m 6XV1843-5FH10-0CCO		
	Prefabricated singlemode glass fiber optic cable, SC/ST/BFOC, 9/125, with 1 × SC duplex connector and 2 × ST/BFOC connectors	1.0 m 6XV1843-5FH10-0CB0		
	Prefabricated singlemode glass fiber optic cable, SC/LC, 9/125, with 1 × SC duplex connector and 1 × LC duplex connector	1.0 m 6XV1843-5FH10-0CA0		
	Prefabricated singlemode glass fiber optic cable, ST/BFOC/LC, 9/125, with 2 × ST/BFOC connectors and 1 × LC duplex connector	1.0 m 6XV1843-5FH10-0AB0		
	Prefabricated singlemode glass fiber optic cable, LC/LC, 9/125, with 2 × LC duplex connectors	1.0 m 6XV1843-5FH10-0AA0		
	Single-mode fiber optic cord LC/LC; 9/125, pre-assembled with 2 × 2 LC full duplex connectors, length 2.0 m	2.0 m 6XV1843-5FH20-0AA0		
	Pre-assembled single-mode fiber optic cord LC/LC; 9/125, pre-assembled with 2 × 2 LC full duplex connectors	3.0 m 6XV1843-5FH30-0AA0		
Special bus cable				
	SIENOPYR Fiber Optic Marine Cable	Fiber optic cable for routing on ships and offshore platforms, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1830-0NH10	
POF and PCF fiber optic cables				
	POF Standard Cable GP 980/1000 ²⁾	Fiber optic cable with polyoptical fibers, for fixed installation indoors, UL approval, sold by the meter, max. delivery unit 500 m, minimum order quantity 20 m	6XV1874-2A	
	POF Trailing Cable 980/1000 ²⁾	Fiber optic cable with polyoptical fibers, for moving applications (e.g., application in cable carriers), sold by the meter, max. delivery unit 500 m, minimum order quantity 20 m	6XV1874-2B	
	PCF Standard Cable GP 200/230 ²⁾	PCF fiber optic cable with plastic cladding, for fixed installation indoors and outdoors, UL approval, sold by the meter, max. delivery unit 2 000 m, minimum order quantity 20 m	6XV1861-2A	
		Prefabricated with 2 × 2 ST/BFOC connectors, preferred length, pulling aid	75 m	6XV1861-3AN75
			100 m	6XV1861-3AT10
			150 m	6XV1861-3AT15
			200 m	6XV1861-3AT20
250 m	6XV1861-3AT25			
	PCF Trailing Cable 200/230 ²⁾	PCF fiber optic cable with plastic cladding, used for high mechanical loads and moving applications (e.g., cable carriers), no UL approval, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1861-2C	
		Prefabricated with 2 × 2 ST/BFOC connectors, preferred length, pulling aid	75 m	6XV1861-3CN75
			100 m	6XV1861-3CT10
150 m	6XV1861-3CT15			
	PCF Trailing Cable GP200/230 ²⁾	PCF fiber optic cable with plastic cladding, used for high mechanical loads and moving applications (e.g., cable carriers), UL approval, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1861-2D	













Electrical/Optical Industrial Ethernet (IE) plugs				
	Product	Comments		Article number ¹⁾
IE FC RJ45 plug 2 × 2				
	IE FC RJ45 Plug 180	RJ45 data connector, for connecting to IE FC TP cables 2 × 2, suitable for fast assembly with the FastConnect system, 180° cable outlet	1 unit	6GK1901-1BB10-2AA0
			10 units	6GK1901-1BB10-2AB0
			50 units	6GK1901-1BB10-2AE0
	IE FC RJ45 Plug 90	90° cable outlet	1 unit	6GK1901-1BB20-2AA0
			10 units	6GK1901-1BB20-2AB0
			50 units	6GK1901-1BB20-2AE0
	IE FC RJ45 Plug 145	145° cable outlet	1 unit	6GK1901-1BB30-0AA0
			10 units	6GK1901-1BB30-0AB0
			50 units	6GK1901-1BB30-0AE0
	IE RJ45 Port Lock	RJ45 port lock with key for mechanical locking of RJ45 ports	1 unit	6GK1901-1BB50-0AA0
Elektrische/Optische Industrial Ethernet (IE)-Stecker				
IE FC RJ45 plug 4 × 2				
	IE FC RJ45 Plug 180	Cat6A RJ45 data connector, for connecting to IE FC TP cables 4 × 2, AWG24, suitable for fast assembly with the FastConnect system	1 unit	6GK1901-1BB12-2AA0
			10 units	6GK1901-1BB12-2AB0
			50 units	6GK1901-1BB12-2AE0
IE FC Keystone RJ45 4 × 2				
	IE FC Keystone RJ45 4 × 2	Field assembly RJ45 outlet, 8-pole, Cat6A, metal enclosure, FC quick connection method, for standard rail mounting and 19" panel	1 unit	6GK1901-0BE10-0AA0
	IE Cable SFP+/SFP+	Prefabricated IE cable with SFP-plus connectors, 1 pack = 1 unit	1 m	6GK5980-3CB00-0AA1
			2 m	6GK5980-3CB00-0AA2
			7 m	6GK5980-3CB00-0AA7
	FO LC Coupler	Plastic enclosure, for mounting in 19" module frame	5 units	6GK1901-0RP10-0AA0
	19" Module Frame 1RU	Module support for mounting of IE RJ45 Keystone or FO LC coupler, mounting in 19" enclosure	1 unit	6GK1901-0AM00-0AA0
	CU/FO Modular Outlet	Modular outlet for mounting of IE RJ45 Keystone or FO LC Coupler, for standard rail mounting	1 unit	6GK1901-1BE00-0AA4
IE push pull plug PRO				
	IE FC RJ45 Plug PRO	FastConnect RJ45 data connector for on-site assembly to IE FC TP cable 2 × 2, field assembly connector for push pull device connection with high degree of protection	1 unit	6GK1901-1BB20-6AA0
	IE FC RJ45 Plug PRO	RJ45 push pull connector for on-site assembly to IE FC TP cable 2 × 2 and IE FC TP cable 4 × 2, metal enclosure, IP65	1 unit	6GK1901-1BB21-6AA0
	IE RJ45 Plug PRO	RJ45 data connector for on-site assembly to TP cables 2 × 2, field assembly connector for push pull device connection with high degree of protection	1 unit	6GK1901-1BB10-6AA0
	IE SC RJ POF Plug PRO	SC RJ plug-in connector for POF fiber optic cable, field assembly connector for push pull device connection with high degree of protection, for SCALANCE X-200IRT PRO switches and SIMATIC ET 200pro	1 unit	6GK1900-0MB00-6AA0
	IE SC RJ PCF Plug PRO	SC RJ plug-in connector for PCF fiber optic cable, field assembly connector for push pull device connection with high degree of protection, for SCALANCE X-200IRT PRO switches	1 unit	6GK1900-0NB00-6AA0
	Power Plug PRO	Power plug-in connector, 5-pin, field assembly connector for push pull device connection with high degree of protection, for power supply with 2 × 24 V DC	1 unit	6GK1907-0AB11-6AA0
	IE RJ45 Coupler PRO	RJ45 push pull coupler for on-site assembly with IE FC RJ45 plug PRO, metal enclosure, IP65	1 unit	6GK1901-0BP10-6AA0




Electrical/Optical Industrial Ethernet (IE) plugs				
	Product	Comments		Article number ¹⁾
Modular outlet				
	IE FC RJ45 Modular Outlet	Without replaceable insert	1 unit	6GK1901-1BE00-0AA0
		With 2FE insert, replaceable insert for 2 × 100 Mbps interfaces	1 unit	6GK1901-1BE00-0AA1
		With 1GE insert, replaceable insert for 1 × 1 000 Mbps interface	1 unit	6GK1901-1BE00-0AA2
	IE FC RJ45 Modular Outlet Insert 2FE	With power insert, replaceable insert for 1 × 24 V DC and 1 × 100 Mbps interface	1 unit	6GK1901-1BE00-0AA3
		Replaceable insert for FC modular outlet base, 2 × RJ45 for 2 × 100 Mbps interfaces	4 units	6GK1901-1BK00-0AA1
	IE FC RJ45 Modular Outlet Insert 1GE	Replaceable insert for FC modular outlet base, 1 × RJ45 for 1 × 1 000 Mbps interface	4 units	6GK1901-1BK00-0AA2
RJ45 outlet				
	IE FC Outlet RJ45	For connection of Industrial Ethernet FC cables and TP cords	1 unit	6GK1901-1FC00-0AA0
M12 connectors and couplers				
	IE FC M12 Plug PRO (D-coded)	M12 plug-in connector 2 × 2 (D-coded) with high degree of protection, 4-pin, for connecting electrical cables to SCALANCE X208PRO and SCALANCE XP-200, ET 200pro PN or ET 200eco PN, suitable for fast assembly with the FastConnect system, pin insert	1 unit	6GK1901-0DB20-6AA0
			8 units	6GK1901-0DB20-6AA8
	IE M12 Panel Feedthrough (D-coded)	Cabinet bushing 2 × 2 for conversion of M12 (D-coded), connection system (IP65) to RJ45 connection system (IP20), socket insert	5 units	6GK1901-0DM20-2AA5
		IE M12 Panel Feedthrough PRO (D-coded)	Cabinet bushing 2 × 2 for conversion of M12 (D-coded), connection system (IP65) to M12 (D-coded) connection system (IP65), socket insert	5 units
	IE FC M12 Plug PRO 4 × 2 (X-coded)	Cat6A M12 plug-in connector 4 × 2 (X-coded) with high degree of protection (IP65), 8-pin, for connecting electrical cables to SCALANCE W and SCALANCE XP-200 (Gigabit M12 interface), suitable for fast assembly with the FastConnect system, pin insert	1 unit	6GK1901-0DB50-6AA0
			8 units	6GK1901-0DB50-6AA8
	IE M12 Panel Feedthrough (X-coded)	Cabinet bushing 4 × 2 for conversion of M12 (X-coded), connection system (IP65) to RJ45 connection system (IP20), Cat6A, socket insert	5 units	6GK1901-0DM40-2AA5
	IE FC M12 Cable Connector PRO (X-coded)	M12 plug-in connectors 4 × 2 (X-coded), for assembly in the field, socket, IP65/67, Cat6A, socket insert	1 unit	6GK1901-0DB40-6AA0
			8 units	6GK1901-0DB40-6AA8
	Control M12 Plug PRO (A-coded)	Connection plug for assembly in the field (A-coded), for connecting IO link sensors/actuators, 5-pole, pin insert	1 unit	6GK1908-0DB10-6AA0
	Control M12 Cable Connector PRO (A-coded)	Connection socket for assembly in the field (A-coded), for connecting IO link sensors/actuators, 5-pole, socket insert	1 unit	6GK1908-0DC10-6AA0
	Signaling Contact M12 Cable Connector PRO (B-coded)	M12 connection socket (B-coded) for signaling contact, 5-pin, for connecting to SCALANCE X208PRO, socket insert	3 units	6GK1908-0DC10-6AA3
	Power M12 Cable Connector PRO (A-coded)	M12 power connection socket (A-coded), 4-pin, for connecting to SCALANCE W-700/X208PRO and SCALANCE XP-200 for 24 V DC power supply, socket insert	3 units	6GK1907-0DC10-6AA3
	Power M12 Plug PRO (A-coded)	M12 power plug-in connector (A-coded), 4-pin, for connecting to Power Supply PS791-1PRO for 24 V DC power supply, pin insert	3 units	6GK1907-0DB10-6AA3
	Power M12 Plug PRO (L-coded)	M12 connector plug (L-coded) for ET 200 with axial cable outlet for field assembly, pin insert	1 unit	6GK1906-0EA00
	Power M12 Cable Connector PRO (L-coded)	M12 cable connector (L-coded) for ET 200 with axial cable outlet for field assembly, socket insert	1 unit	6GK1906-0EB00
	Power M12 Cable Connector PRO (S-coded)	M12 cable connector (S-coded) for SCALANCE PSP9230 PoE with axial cable outlet, female contact insert, 230 AC	1 unit	6GK1907-0DC00-6AA4
	M12 Power T-Tap	M12 Power T-Tap PRO (A-coded), power T-piece for SCALANCE XP-200 with 2 × M12 female contact inserts and 1 × M12 male contact insert, pin insert	5 units	6GK1907-0DC00-6AA5

Electrical/Optical Industrial Ethernet (IE) plugs				
	Product	Comments		Article number ¹⁾
FO connectors (ST/BFOC, SC and LC)				
	FC FO LC Plug	For on site assembly on FC fiber optic cables (62.5/200/230) (duplex plugs + cleaning cloths)	10 units	6GK1900-1RB00-2AB0
	FC SC Coupler	SC duplex coupler for FastConnect assembly	5 units	6GK1900-1LP00-0AB0
	FC ST/BFOC Plug	ST/BFOC plug-in connector, for connection of glass fiber optic cables, suitable for fast assembly with the FastConnect FO system, cleaning cloths	20 units	6GK1900-1GB00-0AC0
	FC ST/BFOC Coupler	ST/BFOC coupler for FastConnect assembly	5 units	6GK1900-1GP00-0AB0
	Multimode FO ST/BFOC Connector Set	ST/BFOC connector set for connection of glass fiber optic cables	20 units	6GK1901-0DA20-0AA0
	FC FO Termination Kit (ST/BFOC)	Assembly case for on-site assembly of FC ST/BFOC connectors to FC fiber optic cables, including a stripping tool, Kevlar shears, fiber breaking tool and microscope	1 unit	6GK1900-1GL00-0AA0
	FC FO Termination Kit (LC)	FC LC plug assembly case for on-site assembly of FC LC connectors to FC fiber optic cables	1 unit	6GK1900-0RL00-0AA0
	IE SC RJ POF Plug PRO	SC RJ plug-in connector for POF fiber optic cable, field assembly connector for push pull device connection with high degree of protection	1 unit	6GK1900-0MB00-6AA0
	IE SC RJ POF Plug	SC RJ plug-in connector for POF fiber optic cables	20 units	6GK1900-0MB00-0AC0
	IE SC RJ PCF Plug PRO	SC RJ plug-in connector for PCF fiber optic cables, field assembly connector for push pull device connection with high degree of protection	1 unit	6GK1900-0NB00-6AA0
	IE SC RJ PCF Plug	SC RJ plug-in connector for PCF fiber optic cables	10 units	6GK1900-0NB00-0AC0
	Multimode FO LC Duplex Plug	LC connector set, for connecting to Ethernet/PROFINET devices with integrated optical multimode interface (SCALANCE XR-300EEC, XR-300, X308-2M)	1 unit	6GK1901-0RB10-2AB0

Electrical PROFIBUS (PB) cables				
	Product	Comments	Article number ¹⁾	
PROFIBUS bus cables				
	PB FC Standard Cable GP	Standard bus cable, with special design for fast assembly, for permanent installation, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1830-0EH10	
	PB FC Standard Cable GP	Standard bus cable, 2-wire, in preferred length, shielded, special design for fast assembly	20 m	6XV1830-0EN20
			50 m	6XV1830-0EN50
			100 m	6XV1830-0ET10
			200 m	6XV1830-0ET20
			500 m	6XV1830-0ET50
			1 000 m	6XV1830-0EU10
	PB FC Standard Cable IS GP	Standard bus cable, for fast assembly, used in intrinsically safe distributed I/O systems, for permanent installation, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1831-2A	
	PB FC Robust Cable	Special bus cable, used in environments subject to chemical and mechanical loads, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1830-0JH10	
	PB FC Food Cable	PB bus cable, for use in the ein, sold by the meter, max. delivery quantity 1 000 m, minimum order quantity 20 m	6XV1830-0GH10	
	PB FC Ground Cable	Special bus cable, with additional protective jacket, used for installation in the ground, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1830-3FH10	
	PB FC Flexible Cable	Flexible bus cable, for occasionally moved machine parts, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1831-2K	
	PB FC Trailing Cable	Highly flexible bus cable, continuous motion control in a cable carrier, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1830-3EH10	
	PB FC Trailing Cable	Highly flexible bus cable, continuous motion control in a cable carrier, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1831-2L	
	PB Festoon Cable GP	Flexible bus cable, specially used for festoon suspension, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1830-3GH10	
	PB FC FRNC Cable GP	Heavily flame-retardant and halogen-free bus cable, suitable for use in buildings, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1830-0LH10	
	PB Torsion Cable	Flexible bus cable, used in moved machine parts, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1830-0PH10	
	PB Hybrid Standard Cable GP	Hybrid cable, data and power wires, trailable, for supplying data and power to ET 200pro, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1860-2R	
	PB Hybrid Robust Cable	Hybrid cable, data and power wires, robust, for supplying data and power to ET 200pro under conditions with high mechanical load, cable resistant to splatter in accordance with HD22.2 S3 / 5, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1860-2S	
	PB FC Process Cable, Blue	Bus cable for IEC61158-2/Ethernet APL line GP 2-WISE (IEC TS 60079-47) APL Type A, 2-wire, for Ex applications, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1830-5EH10	
	PB FC Process Cable, Black	Bus cable for IEC 61158-2/Ethernet APL line GP 2-WISE (IEC TS 60079-47) APL Type A, 2-wire, for non-Ex applications, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1830-5FH10	
	Foundation Fieldbus Cable, Blue	Bus cable for IEC 61158-2, 2-wire, for Ex applications, stranded drain wire, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1830-5GH10	
	Foundation Fieldbus Cable, Yellow	Bus cable for IEC 61158-2, 2-wire, for non-Ex applications, stranded drain wire, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1830-5HH10	
Special bus cables				
	SIENOPYR PROFIBUS Marine Cable	Bus cable, 2-wire, for installation on ships and offshore platforms, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1830-0MH10	

Electrical PROFIBUS (PB) cables				
	Product	Comments	Article number ¹⁾	
ECOFAST bus cables				
	PROFIBUS ECOFAST Cable	Open-ended ECOFAST hybrid cable, data and power wires, for connecting ECOFAST devices, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	0.5 m	6XV1830-7AH10
			1.0 m	6XV1830-7BH10
		Prefabricated with ECOFAST plug and socket, fixed length	1.5 m	6XV1830-7BH15
			3.0 m	6XV1830-7BH30
			5.0 m	6XV1830-7BH50
			10 m	6XV1830-7BN10
			15 m	6XV1830-7BN15
			20 m	6XV1830-7BN20
ECOFAST bus cables (continued)				
	PROFIBUS ECOFAST Hybrid Cable GP	Open-ended trailing-type cable with 4 × Cu and 2 × Cu, shielded, with UL approval, sold by the meter, max. delivery unit 1 000 m, minimum order quantity 20 m	6XV1860-2P	
Plug-in cables (prefabricated cables)				
	PB Plug-in Cable 830-1T	Prefabricated plug-in cable, with two 9-pin sub-D connectors, for connection of PROFIBUS devices to OLM or OBT, preferred length	1.5 m	6XV1830-1CH15
			3.0 m	6XV1830-1CH30
	PB Plug-in Cable 830-2	Prefabricated plug-in cable including PROFIBUS standard cable with two 9-pin connectors, for connection of PROFIBUS devices (e.g., HMI) to automation devices, preferred length	3.0 m	6XV1830-2AH30
			5.0 m	6XV1830-2AH50
			10 m	6XV1830-2AN10
	PB M12 Plug-in Cable (B-coded)	Prefabricated, flexible plug-in cable, with two 5-pin M12 male/female connectors (B-coded), for connecting PROFIBUS devices (e.g., SIMATIC ET 200), in IP65 degree of protection, preferred length	0.3 m	6XV1830-3DE30
			0.5 m	6XV1830-3DE50
			1.0 m	6XV1830-3DH10
			1.5 m	6XV1830-3DH15
			2.0 m	6XV1830-3DH20
			3.0 m	6XV1830-3DH30
			5.0 m	6XV1830-3DH50
10 m	6XV1830-3DN10			
15 m	6XV1830-3DN15			
Optical PROFIBUS (PB) cables				
FO cables				
	PB POF Standard Cable	Robust round cable with 2 plastic fiber optic cores, PVC outer sheath and PA inner sheath, for indoor installation, sold by the meter, max. delivery unit 500 m, minimum order quantity 20 m	6XV1821-0AH10	
			Prefabricated with 2 × 2 ST/BFOC connectors, preferred length, lash length 20 cm each, for connecting OLM/P	1.0 m
		2.0 m		6XV1821-0BH20
		5.0 m		6XV1821-0BH50
		10 m		6XV1821-0BN10
		15 m		6XV1821-0BN15
		20 m		6XV1821-0BN20
		25 m		6XV1821-0BN25
		30 m		6XV1821-0BN30
		50 m		6XV1821-0BN50
		65 m		6XV1821-0BN65
		80 m		6XV1821-0BN80
		PB PCF Standard Cable	Prefabricated PCF fiber optic cable with 2 cores, PVC outer jacket, for covering longer distances up to 400 m, with 2 × 2 ST/BFOC connectors, lash length 20 cm each, with insertion tool mounted on one end, for connecting OLM/P, preferred length	75 m
100 m	6XV1821-1BT10			
150 m	6XV1821-1BT15			
200 m	6XV1821-1BT20			
250 m	6XV1821-1BT25			
300 m	6XV1821-1BT30			
PB PCF Standard Cable GP 200/230	Standard cable, segmentable, sold by the meter, max. delivery unit 2 000 m, minimum order quantity 20 m	6XV1861-2A		
		Prefabricated with 2 × 2 ST/BFOC connectors, preferred length	75 m	6XV1861-3AN75
			100 m	6XV1861-3AT10
			150 m	6XV1861-3AT15
			200 m	6XV1861-3AT20
			250 m	6XV1861-3AT25

Electrical/Optical PROFIBUS (PB) connectors				
	Product	Comments		Article number ¹⁾
PROFIBUS bus connectors				
	PB FC RS 485 Plug 180	FastConnect bus connector with insulation displacement method, max. transfer rate 12 Mbps, 180° cable outlet (without PG interface)	1 unit	6GK1500-0FC10
	PB FC RS 485 Plug 90	90° cable outlet (without PG interface)	1 unit	6ES7972-0BA52-0XA0
		90° cable outlet (without PG interface, grounding via control cabinet contact surface)	100 units	6ES7972-0BA52-0XB0
		90° cable outlet (with PG interface)	1 unit	6ES7972-0BA70-0XA0
		90° cable outlet (with PG interface)	100 units	6ES7972-0BB52-0XA0
		90° cable outlet (with PG interface, grounding via control cabinet contact surface)	1 unit	6ES7972-0BB70-0XA0
	PB FC RS 485 Plug 35	35° cable outlet (without PG interface)	1 unit	6ES7972-0BA61-0XA0
		35° cable outlet (with PG interface)	1 unit	6ES7972-0BB61-0XA0
	PB RS 485 Plug 180	Bus connector in screw-type connection system, max. transmission rate 12 Mbps, 180° cable outlet (without PG interface, metal enclosure)	1 unit	6GK1500-0EA02
	PB RS 485 Plug 90	90° cable outlet (without PG interface)	1 unit	6ES7972-0BA12-0XA0
		90° cable outlet (with PG interface)	1 unit	6ES7972-0BB12-0XA0
	PB RS 485 Plug 35	35° cable outlet (without PG interface)	1 unit	6ES7972-0BA42-0XA0
		35° cable outlet (with PG interface)	1 unit	6ES7972-0BB42-0XA0
	PB RS 485 Plug 30	30° cable outlet (low-cost version, max. transmission rate 1.5 Mbps)	1 unit	6ES7972-0BA30-0XA0
	ECOFAST Hanbrid Connector	PROFIBUS bus connector Cu with 2 × Cu shielded and 4 × Cu 1.5 mm ² , contact type: for connecting to ECOFAST hybrid cables, transmission of data and power, tool: crimping tool, with installation instructions and male contact insert	5 units	6GK1905-0CA00
		With installation instructions and female contact insert	5 units	6GK1905-0CB00
		PROFIBUS ECOFAST hybrid plug angled, with 2 × Cu shielded and 4 × Cu 1.5 mm ² , for connecting to ECOFAST hybrid cables, transmission of data and power, with installation instructions and male contact insert	5 units	6GK1905-0CC00
		With installation instructions and female contact insert	5 units	6GK1905-0CD00
	ECOFAST Terminating Plug	Bus terminator plug-in connector for PROFIBUS DP, with 2 × Cu and 4 × Cu 1.5 mm ² , as termination plug-in connector for PROFIBUS DP, male contact insert, integrated termination resistors	1 unit	6GK1905-0DA10
			5 units	6GK1905-0DA00
Connectors for assembly in the field				
	PB FC M12 Plug PRO (B-coded)	Field-assembly M12 connector (B-coded), 5-pin, Metal housing, FastConnect quick connection technology, pin insert, for connecting electrical PB FC bus lines to ET 200pro, suitable for fast assembly with the FastConnect system	1 unit	6GK1905-0EA10-6AA0
			5 units	6GK1905-0EA10
	PB FC M12 Cable Connector PRO (B-coded)	M12 plug-in connector for assembly in the field (B-coded), 5-pin, metal enclosure, FastConnect connection system, female contact insert, for connecting electrical PB FC bus cables to ET 200pro, suitable for fast assembly with the FastConnect system	1 unit	6GK1905-0EB10-6AA0
			5 units	6GK1905-0EB10
	PB Plastic Fiber Optic, ST/BFOC Connector Set	20 ST/BFOC connectors for assembly of PROFIBUS plastic fiber optic cables for OLM/P	1 unit	6GK1905-1PA00
	PCF-ST/BFOC Plug	20 screw connectors for on-site assembly on PCF fiber optic cables, with cleaning material	1 unit	6GK1900-0HB00-0AC0
	7/8" Plug-in Connector	7/8" connection plug with male contact insert, 5-pin, for field assembly, for ET 200	5 units	6GK1905-0FA00
		7/8" connection plug with female contact insert, 5-pin, for field assembly, for ET 200	5 units	6GK1905-0FB00

Electrical/Optical Accessories for Industrial Ethernet (IE) and PROFIBUS (PB)			
	Product	Comments	Article number ¹⁾
	IE FC Stripping Tool	Pre-adjusted stripping tool for fast stripping of Industrial Ethernet FC cables	6GK1901-1GA00
	IE FC Blade Cassettes	Replacement blade cassette, for IE FC RJ45 outlet, ELS TP40, 5 units, 12 mm	6GK1901-1GB00
	IE FC Blade Cassettes	Replacement blade cassette, for IE FC RJ45 plugs and IE FC RJ45 modular outlet, 5 units, 5 mm	6GK1901-1GB01
	IE SC RJ POF Refill Set	Refill set for termination kit SC RJ POF plug consisting of abrasive paper and grinding disc (set of 5)	6GK1900-0MN00-0AA0
	PB FastConnect Stripping Tool	Pre-adjusted stripping tool for fast stripping of PROFIBUS FastConnect bus cables	6GK1905-6AA00
	PB FastConnect Blade Cassettes	Spare blade cassettes for PROFIBUS FastConnect stripping tool, 5 units	6GK1905-6AB00
	PB Plastic Fiber Optic, Stripping Tool Set	Tools for removing the outer sheath or core sheath of PROFIBUS plastic fiber optic cables	6GK1905-6PA10
	PB Plastic Fiber Optic, Crimping Tool ST/BFOC	For assembly of ST/BFOC connectors on PROFIBUS plastic fiber optic cables	6GK1905-6PB00
	PB Plastic Fiber Optic, Polishing Set ST/BFOC	Polishing set for grinding and polishing the ST/BFOC connector face, for PROFIBUS plastic fiber optic cables with OLM/P	6GK1905-6PS00
	7/8" Power T-Tap PRO	Power T-piece with two 7/8" female contact inserts and one 7/8" male contact insert, to connect and distribute power to ET 200pro modules, each 5-pin, 1 package = 5 units	6GK1905-0FC00
	FC FO Termination Kit (ST/BFOC)	Assembly case for on-site assembly of FC ST/BFOC connectors to FC fiber optic cables, including a stripping tool, Kevlar shears, fiber breaking tool and, microscope	6GK1900-1GL00-0AA0
	FC FO Termination Kit (LC)	FC FO termination kit, FC LC plug assembly case for on-site assembly of FC LC connectors to FC fiber optic cables	6GK1900-0RL00-0AA0
	Termination Kit SC RJ POF Plug	Assembly case for on-site assembly of SC RJ POF connectors, including a stripping tool, Kevlar shears, SC RJ grinding disc, abrasive paper, grinding base, and microscope	6GK1900-0ML00-0AA0
	Termination Kit SC RJ PCF Plug	Assembly case for on-site mounting of SC RJ PCF connectors, including a stripping tool, buffer stripping tool, Kevlar shears, fiber breaking tool, and microscope	6GK1900-0NL00-0AA0
	Termination Kit Simplex PCF Plug	Assembly case for on-site assembly of PCF simplex connectors, including a stripping tool, buffer stripping tool, Kevlar shears, fiber breaking tool, crimping tool, and microscope	6GK1900-0KL00-0AA0
	Termination Kit PCF-ST/BFOC Plug	Assembly case for on-site assembly of PCF-ST/BFOC connectors, including a stripping tool, buffer stripping tool, Kevlar shears, fiber breaking tool, and microscope	6GK1900-0HL00-0AA0

¹⁾ Current ordering data can be found on the Internet:
www.siemens.com/industrymall
 Conditions of sale and delivery can be found at:
https://mall.industry.siemens.com/legal/ww/en/terms_of_trade_en.pdf

²⁾ Also suitable for PROFIBUS

You can find additional information on the SIMATIC NET range of cabling products at:
www.siemens.com/fastconnect

Find the right FastConnect components directly in the TIA Selection Tool configurator:
<https://www.siemens.com/tstcloud/?node=CablesAndPlugs>

You can find more detailed manuals online via the direct links:

[SIMATIC NET Industrial Ethernet/PROFINET Passive network components](#)

[SIMATIC NET PROFIBUS Network Manual](#)

[SIMATIC NET Industrial Ethernet/PROFINET Industrial Ethernet System Manual](#)

Notes:

Cables sold by the meter are always supplied on wooden drums for lengths longer than 300 m.

You can receive technical advice on the SIMATIC NET range of cabling products from:
Cabling.industry@siemens.com

Published by
Siemens AG

Siemens AG
Digital Industries
Process Automation
Östliche Rheinbrückenstr. 50
76187 Karlsruhe, Germany

Article no.: 6ZB5530-ODN02-0AB4
BR 1123 PoD 26 En
Produced in Germany
© Siemens 2023

Security Information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, systems, machines and networks.

In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial security concept. Siemens' products and solutions constitute one element of such a concept.

Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place.

For additional information on industrial security measures that may be implemented, please visit **<https://www.siemens.com/industrialsecurity>**.

Siemens products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats.

To stay informed about product updates, subscribe to the Siemens Industrial Security RSS Feed under **<https://www.siemens.com/industrialsecurity>**.

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

All product designations may be trademarks or product names of Siemens AG or other companies whose use by third parties for their own purposes could violate the rights of the owners.

