



Certificate of Compliance

Certificate: 1552060 (LR 12730-311)

Master Contract: 165071

Project: 2553242

Date Issued: August 21, 2012

Issued to: Siemens AG

**I IA CE CP R&D-VI 4
Werner-von-Siemens-Strasse 48
Amberg, 92220
Germany
Attention: Klaus Drutschmann**

The products listed below are eligible to bear the CSA Mark shown



Pierre-Yves Despatis

Issued by: Pierre-Yves Despatis

PRODUCTS

CLASS 3211 03 - INDUSTRIAL CONTROL EQUIPMENT - Motor Controllers - Auxiliary Devices

Thermal Overload Relays, adjustable, open type, 600V ac 3-phase:

- Type 3UA58, 4A up to 88A in 12 setting ranges, control circuit (1 NO and 1 NC) R300/B600 same polarity, R150/B150 opposite polarity per pole
- Type 3UW17, 4A up to 88A in 12 setting ranges; control conduit (change over contact) B600/R300

Connection supports, Type 3UX1421, may be provided as accessories.

Notes:

1. The type designation may be completed with numbers and letters indicating electrical and mechanical details.
2. The relays are intended for use in combination with this manufacturer's Certified contactors or for separate use, where the acceptability of the combination is to be determined by CSA International.
3. The relays are ambient temperature compensated.

Nomenclature breakdown:



Certificate: 1552060 (LR 12730-311)

Master Contract: 165071

Project: 2553242

Date Issued: August 21, 2012

3UA58	13	-2E
I	II	III

I Basic type designation:

3UA58, 3UW17

II Indicates open type:

00 or 01 Tripping current 125% of dial setting

40 Same as 00

III Indicates setting range:

Identical to catalogue suffix number

F.L.A. Setting Range	Catalogue Suffix Number	Max Series Fuse Size	Max Breaker SRE (Amperes)
4 - 6.3	-1G	25	25
12.5 - 20	-2B	80	80
16 - 25	-2C	100	100
20 - 32	-2D	125	125
25 - 40	-2E	150	150
32 - 50	-2F	200	200
50 - 63	-2P	250	250
40 - 57	-2T	225	225
63 - 80	-2U	300	300
57 - 70	-2V	250	250
11 - 17	-8A	60	60
70 - 88	-8W	350	350

APPLICABLE REQUIREMENTS

CSA-C22.2 No. 14-10 - Industrial Control Equipment



Descriptive Report and Test Results

MASTER CONTRACT: 165071

REPORT: 1552060

PROJECT: 2553242

- Edition 1:** January 26, 1993; Application No. LR 12730-311 (KEMA Job No. 91.5456)
Issued by R.M.M.A. Geuijen; Reviewed by J. Pankowski
- Edition 2:** May 29, 1996; Application No. LR 12730-353 (KEMA Job No. 96.1192)
Issued by R.M.M.A. Geuijen; Reviewed by J. Pankowski
- Edition 3:** September 28, 2004; Project 1552060 - Montreal
Issued by M. Legault, Eng
- Edition 4:** December 11, 2008; Project 2095641 - Montreal
Issued by J.-C. Chow, Eng.
- Edition 5:** August 21, 2012; Project 2553242 – Montréal
Issued by P-Y Despatis, Eng. ; Reviewed by J.-C. Chow, Eng.

Report pages reissued

Contents: Certificate of Compliance - Pages 1 to 2
Supplement to Certificate of Compliance - Page 1
Description and Tests - Pages 1 to 9
Att 1 Figures - Fig. Nos. 1 to 3, 3A and 4 (Labeled as LR 12730)
Att 2 Illustrations - Ill. Nos. 1 to 5 (Labeled as LR 12730)
Att 3 Test Sheets - Nos. T2 to T15 (Labeled as LR 12730)
Att 3 Test Sheets - Nos. T16 and T17

PRODUCTS

CLASS 3211 03 - INDUSTRIAL CONTROL EQUIPMENT - Motor Controllers - Auxiliary Devices

Thermal Overload Relays, adjustable, open type, 600V ac 3-phase:

Type 3UA58, 4A up to 88A in 12 setting ranges, control circuit (1 NO and 1 NC) R300/B600 same polarity, R150/B150 opposite polarity per pole

Type 3UW17, 4 A up to 88 A in 12 setting ranges; control conduit (change over contact) B600/R300.

Connection supports, Type 3UX1421, may be provided as accessories.

Notes:

The posted report does not represent the full certification report.

865 Ellingham Street, Pointe-Claire, Quebec, Canada H9R 5E8
Telephone: 514.694.8110 1.800.463.6727 Fax: 514.694.5001 www.csagroup.org

- 1 The type designation may be completed with numbers and letters indicating electrical and mechanical details.
- 2 The relays are intended for use in combination with this manufacturer's Certified contactors or for separate use, where the acceptability of the combination is to be determined by CSA International.
- 3 The relays are ambient temperature compensated.

Nomenclature breakdown:

3UA58 13 -2E
 I II III

I Basic type designation:
 3UA58, 3UW17

II Indicates open type:
 00 or 01 Tripping current 125% of dial setting
 40 Same as 00

III Indicates setting range:
 Identical to catalogue suffix number

<u>F.L.A. Setting</u> <u>Range</u>	<u>Catalogue Suffix</u> <u>Number</u>	<u>Max Series Fuse</u> <u>Size</u>	<u>Max Breaker SRE</u> <u>(Amperes)</u>
4 - 6.3	-1G	25	25
12.5 - 20	-2B	80	80
16 - 25	-2C	100	100
20 - 32	-2D	125	125
25 - 40	-2E	150	150
32 - 50	-2F	200	200
50 - 63	-2P	250	250
40 - 57	-2T	225	225
63 - 80	-2U	300	300
57 - 70	-2V	250	250
11 - 17	-8A	60	60
70 - 88	-8W	350	350

APPLICABLE REQUIREMENTS

- CAN/CSA-C22.2 No. 0-10 - General Requirements - Canadian Electrical Code, Part II
- CSA-C22.2 No. 14-10 - Industrial Control Equipment