

SIEMENS

Ingenuity for life



Top values in precision and reliability

Temperature measurement
with SITRANS T

[siemens.com/processinstrumentation](https://www.siemens.com/processinstrumentation)

Temperatures firmly under control


Top process quality and efficiency are key factors for success in the process industry, and achieving them requires absolutely accurate and reliable process instrumentation. The best example of this is SITRANS T, our comprehensive product family for temperature measurement.

First choice for all requirements in the process industry

Whether as individual components or a complete solution, SITRANS T definitely has the right devices for your requirements. Our product family offers temperature sensors and transmitters for every application in the process industry, even under extreme conditions – including general purpose, intrinsically safe, and explosion-proof, and with globally recognized certificates. Naturally we will support you throughout the entire lifecycle of your devices with expert service and support.

Impressively communicative

With SITRANS T, you benefit from end-to-end ease of use and the highest transparency. Powerful software and a comprehensive communications capability ensure simple, highly efficient device integration and configuration.






Benefits at a glance

- Highest flexibility because devices are available as a complete measuring point or transmitter for head, rail, or field-mount installation
- Superior communications capability based on industrial standards such as 4–20 mA, HART, PROFIBUS PA, and FOUNDATION Fieldbus
- Simple integration into SIMATIC PCS 7 and all common process control systems
- Support for planning, parameterization, commissioning, diagnostics, and maintenance through SIMATIC PDM (Process Device Manager)
- Device operation via HART and PROFIBUS PA through the use of EDDs
- Devices for SIL applications usable up to level 2/3

SITRANS T

temperature measurement

As the perfect basis for highly precise and reliable temperature measurements, the solutions in the SITRANS T family are a good choice for a wide range of applications. They also support operation and monitoring on-site, since the process variables can be comfortably read on an optional display.



SITRANS T is the first choice wherever intelligent processing of readings is required. The measurement status is easy to monitor remotely or locally. Functional safety permits SIL 2/3 applications. Safety and accuracy have been significantly improved with the option of connecting 2 x 4-wire resistance thermometers, as well as through simple

sensor-transmitter matching. As an added benefit, maintenance is supported by a two-color diagnostics LED and test pins: suspect measurements can be detected at a glance – and with one touch, the current loop can be measured without any interruption.



The complete program for a wide range of applications

SITRANS T products are suitable for a variety of applications. Temperature sensors and head transmitters can be integrated directly into the process. Under adverse conditions, head transmitters can be decoupled from the process and easily replaced with sensors, remote field transmitters or rail transmitters.

SITRANS TR420

High availability is ensured by the new 2 x 4-wire sensor with hot backup

SITRANS TS500

SITRANS TH320/420

Control cabinet junction box

SITRANS TR320/420

SITRANS TS500

Wall mount

SITRANS TF

Whether by wall mount or in the control cabinet – the temperature sensors offer flexible installation.



SITRANS TH

Available in robust die-cast aluminum or long-lasting stainless steel 316 L, the field transmitter in high protection class IP66/67/68 is particularly suitable for use under harsh environmental conditions.



SITRANS TS200

The compact SITRANS TS200 product series offers the same advantages as SITRANS TS100. The only difference is in the design: instead of a flexible cable, the system comes with a fixed connection (M12, Lemo, etc.).

SITRANS TS100

Whether as a basic or mineral-insulated version, SITRANS TS100 supports a wide field of applications and comes with a directly mounted cable. Compression or soldering fittings minimize installation work while the optional adapter simplifies surface measurement. The intrinsically safe version is approved for operation even in zone 0 without an additional thermowell. Here the sensor's excellent response time truly pays off.

SITRANS TR

The rail transmitters offer the same features as SITRANS TH but are deployed close to the process in junction boxes or the control room, thus enabling centralized access to all connected measurement points.



SITRANS TS500

SITRANS TS500 is available in intrinsically safe versions as well as Ex d and supports a wide field of measurements, from simple applications to solutions for harsh environments. It is designed as a modular system of tubular or barstock thermowell, extension, connection head, and optional transmitter and display. This allows standard components to be used for individual applications.



SITRANS T

Despite their compact design for direct installation in the connection head, the transmitters offer a high degree of comfort and safety – for simple applications as well as for PROFIBUS and FOUNDATION Fieldbus installations.



Special devices for food and pharma

The SITRANS T clamp-on sensors for hygienic applications feature a wide range of appropriate process connections for classic temperature measurement. When it comes to accuracy and response time, they are comparable to built-in sensors. They offer obvious advantages, especially for small pipe diameters: no welding or welding validation, no process disturbance, easy pigging, and easy dismantling for recalibration.





SITRANS TS at a glance:



Type	SITRANS TS insert	SITRANS TS100 / SITRANS TS200	SITRANS TS300
	Measuring insert spares Mineral-insulated execution (MIC)	Temperature sensors in cable version Mineral-insulated execution	Temperature sensors for food & beverage/pharma In-pipe or clamp-on
Application	Spares	Plant and machinery construction, bearing temperature, surface measurement	Advanced hygienic requirements
Process connection		Compression or soldering fittings: G [1/4, 1/2]"; 1/2" NPT; M8x1; M18x1.5 Surface mounting adapter for installation on pipes	In-pipe: Clamp-flange, DIN 11851, Varivent, BioControl, Neumo, Ingold, spherical-welding sleeve Clamp-on: Collar 4 ... 57 mm Strap up to 200 mm
Certificates	Europe+IEC EX: • Intrinsic safety "ia", "ic" • Flameproof enclosure "d"; dust protection by enclosure "t"	Europe+IEC EX: • Intrinsic safety "ia", "ic"	
Output	Direct sensor signal 4 ... 20 mA (TH100/TH200) HART (TH300) PA (TH400) FF (TH400)	Direct sensor signal	Direct sensor signal 4 ... 20 mA (TH100/TH200) HART (TH300) PA (TH400) FF (TH400)
Wetted material	SS similar 1.4404 (RTD), 2.4816 (thermocouple) (SS sim. 316L, INCONEL® Alloy 600)	SS similar 1.4404 (RTD), 2.4816 (thermocouple) (SS sim. 316L, INCONEL® Alloy 600)	In-pipe: 1.4404/316L Clamp-on: No wetted parts
Technical data			
Temperature limits*	PT100 Basic: -30 ... +400°C PT100 Extend: -196 ... +600°C Thermocouple: -196 ... +1100°C (depends on type)	PT100 Basic: -30 ... +400°C PT100 Extend: -196 ... +600°C Thermocouple: -196 ... +1100°C (depends on type)	In-pipe: -30 ... +300°C Clamp-on: -20 ... +160°C
Minimum response time $t_{0,5}$	2 ... 6 s	2 ... 6 s	5 s
Degree of protection	IP54	SITRANS TS100: IP54 SITRANS TS200: IP54 (some connectors lower)	IP65 (IP54 for some head types)

* A combination of loads (temperature, flow, vibration, pressure) sometimes lowers these values significantly.
Further temperature limits are the result of the thermowell materials used.
(Example: 1.4571/316Ti is resistant to compression stress up to 450–550°C, material limit: 800°C)

** pending

			
SITRANS TS500	SITRANS TS500	SITRANS TS500	SITRANS TS-Thermowell NEW
Temperature sensors for installation in existing thermowells	Temperature sensors with tubular thermowell for low to medium process load	Temperature sensors with barstock thermowell for high process load	Protective tube made from solid material to DIN 43772 and ASME B40.9
Suitable for thermowells according to DIN 43772 as well as ASME B40.9-2001	Thermowell Form 2 or 3 (tapered) according to DIN 43772 and Form 2N with thread, flange, or without process connection	Thermowell according to DIN 43772, Form 4 for weld-in or Form 4F with flange	
Vessel and pipes	Vessel and pipes	Vessel and pipes	Containers and pipelines
Connection to thermowell: M18x1.5; G 1/2", 1/2" NPT	Compression fitting G 1/2", 1/2" NPT Welded thread G 1/2", G1", 1/2" NPT Welded flange DN25PN40, 1RF150, 1.5RF150, 1.5RF300	Form 4 for weld-in Form 4F with flange: DN25PN40, 1RF150, 1RF300, 1.5RF150, 1.5RF300	For welding to DIN/ASME Thread G, R[1/2", 3/4", 1", 1 1/2"] Thread NPT[1/2", 3/4", 1", 1 1/2"] Thread M[20x1,5; 27x2; 33x2] Flange ASME 3/4"; 1"; 1 1/2"; 2"; [150; 300; 600 lbs]
Europe+IEC EX: • Intrinsic safety "ia", "ic" • Flameproof enclosure "d"; dust protection by enclosure "t" • Non-sparking "n"	Europe+IEC EX: • Intrinsic safety "ia", "ic" • Flameproof enclosure "d"; dust protection by enclosure "t" • Non-sparking "n"	Europe+IEC EX: • Intrinsic safety "ia", "ic" • Flameproof enclosure "d"; dust protection by enclosure "t" • Non-sparking "n"	
Direct sensor signal 4 ... 20 mA (TH100/TH200) HART (TH300) PA (TH400) FF (TH400)	Direct sensor signal 4 ... 20 mA (TH100/TH200) HART (TH300) PA (TH400) FF (TH400)	Direct sensor signal 4 ... 20 mA (TH100/TH200) HART (TH300) PA (TH400) FF (TH400)	
No wetted parts	1.4404, 1.4571 (316L, 316TI)	Form 4F: 1.4404, 1.4571 (316L, 316TI) Form 4 additionally 1.7335, 1.5415 (A 182 F11, A 204 Gr. A)	316L; CS; Hastelloy [C276, C22]; 304; 321; Monel; Duplex, Superdup. div. coatings
PT100 Basic: -30 ... +400°C PT100 Extend: -196 ... +600°C Thermocouple: -196 ... +1100°C (depends on type)	PT100 Basic: -30 ... +400°C PT100 Extend: -196 ... +600°C Thermocouple: -196 ... +1100°C (depends on type)	PT100 Basic: -30 ... +400°C PT100 Extend: -196 ... +600°C Thermocouple: -196 ... +1100°C (depends on type)	Depends on material
Depends on type of thermowell	7...45 s	20 ... 45 s	Depends on shape
IP65 (IP54 for some head types)	IP65 (IP54 for some head types)	IP65 (IP54 for some head types)	All can be implemented, depending on installation

SITRANS TH, TR, TW, and TF at a glance:



Type	SITRANS TH100	SITRANS TH320/ SITRANS TH420	NEW SITRANS TH400
Installation	In the connection head		
	Two-wire		
Input (connectable sensors)	PT100 resistance thermometers	Up to 2 sensors: Resistance thermometers Thermocouples Resistance-type sensors DC sources	Resistance thermometers Thermocouples Resistance-type sensors DC sources
Output	4 ... 20 mA	SITRANS TH320: 4 ... 20 mA, HART 7 SITRANS TH420: HART 7	PROFIBUS PA version FOUNDATION Fieldbus version
Local display			
Power supply	DC 8.5 ... 36 V (30 V for Ex)	DC 7.5 ... 48 V	DC 9 ... 32 V (30 V for Ex and 17.5 V for FISCO)
Housing material	Molded plastic, embedded electronics	Molded plastic, embedded electronics	Molded plastic, embedded electronics
Ambient temperature	−40 ... +85°C	−50 ... +85°C	−40 ... +85°C
Degree of protection	Enclosure: IP68 Terminal: IP00	Enclosure: IP68 Terminal: IP00	Enclosure: IP68 Terminal: IP00
Certificates	Europe (ATEX): Ex ia, ib, ic, Ex n USA (cFMus): IS, NI Canada (cFMus): IS, NI Other certificates: GOST, NEPSI, PESO	Ex: ATEX, IECEx, cFMus, cCSAus, EAC/ EACEx, NEPSI, KCC/KCs, Inmetro, SIL 2/3 Ex i, Ex nA/ec, IS, NI, NIFW Zone 0/1/2, Division 1/2 Marine: DNV-GL, ABS, LR, BV	Europe (ATEX): Ex ia, Ex ib, Ex n USA (cFMus): IS, NI Canada (cFMus): IS, NI Other certificates: GOST, PESO
Operator input			
SIMATIC PDM		HART version	PROFIBUS PA FOUNDATION Fieldbus
Handheld 375		HART version	FF version
AMS		HART version	FF version
SIPROM T and special modem	•	4 ... 20 mA version	
Local configuration using 4 push buttons			



SITRANS TR320 / SITRANS TR420	NEW	SITRANS TF	SITRANS TF320 / SITRANS TF420	SITRANS TO	NEW
On DIN rail		Field device			
Up to 2 sensors: Resistance thermometers Thermocouples Resistance-type sensors DC sources		Resistance thermometers Thermocouples Resistance sensors Direct current/voltage sources	Up to 2 sensors: Resistance thermometers Thermocouples Resistance sensors DC voltage sources	4-channel transmitters for fiber Bragg grating (FBG) sensors (max. 48 per channel)	
SITRANS TH320: 4 ... 20 mA, HART 7 SITRANS TH420: HART 7		Field indicators (LCD only) PROFIBUS PA FOUNDATION field bus	SITRANS TF320: 4 ... 20 mA, HART 7 SITRANS TF420: HART 7	PROFIBUS DP	
			LCD for local operation		
DC 7.5 ... 48 V		DC 11/13.5 ... 35 V (30 V for Ex and 17.5 V for FISCO)	DC 10.5 ... 48 V	DC 24 V \pm 20%	
Molded plastic, embedded electronics		Die-cast aluminum, coated, or stainless steel	Die-cast aluminum, coated, or stainless steel 316 L**		
-50 ... +85°C		-40 ... +85°C	-50 ... +85°C	0 ... +50°C	
IP20		IP67	IP66/67/68	IP20	
Ex: ATEX, IECEx, cFMus, cCSAus, EAC/ EACEx, NEPSI, KCC/KCs, Inmetro, SIL 2/3 Ex i, Ex nA/ec, IS, NI, NIFW Zone 0/1/2, Division 1/2 Marine: DNV-GL, ABS, LR, BV		Europe (ATEX): Ex ia, Ex d, Ex n USA: XP/DIP/NI/IS SIL 2 and SIL 2/3 (4 ... 20 mA/HART) Other certificates: GOST, INMETRO, NEPSI, KOSHA	Ex: ATEX, IECEx, cFMus, cCSAus, EAC/ EACEx, NEPSI, KCC/KCs, Inmetro, SIL 2/3 Ex i, Ex nA/ec, IS, NI, NIFW Zone 0/1/2, Division 1/2 Marine: DNV-GL, ABS, LR, BV**	ATEX/IECEx (as per guidelines according to IEC/EN 50079-28-2015) II (1) G [Ex op is IIC T6 Ga] II (1) D [Ex op is IIIC Da] I (M1) [Ex op is I Ma]	
HART version		HART / PROFIBUS PA / FOUNDATION Fieldbus	HART version		
HART version		HART / FOUNDATION Fieldbus	HART version		
HART version		HART / FOUNDATION Fieldbus	HART version		
4 ... 20 mA version		4 ... 20 mA	4 ... 20 mA version		
		•			

**Published by
Siemens AG 2018**

Process Industries and Drives
Östliche Rheinbrückenstr. 50
76187 Karlsruhe
Germany

Article No.: PDPA-B10330-00-7600
Dispo 27900
WS 05184.0
Printed in Germany
© Siemens AG 2018

Subject to changes and errors. The information provided in this brochure contains descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.

All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.

