

	Output/Type	Rated input voltage (range)	Dimensions in mm (WxHxD)	Article No. Siemens ¹⁾	Short description
Power supplies in special design, for special uses					
	12 V DC/3 A, PSU100D	100 – 240 V AC (85 ... 264 V AC)	97 x 98 x 38	6EP1321-1LD00	<ul style="list-style-type: none"> Low-cost power supply for wall mounting in various installation positions Rugged aluminum enclosure Wide-range input Temperature range from –10 to +70 °C
	12 V DC/8.3 A, PSU100D		97 x 158 x 38	6EP1322-1LD00	
	24 V DC/2.1 A, PSU100D		97 x 128 x 38	6EP1331-1LD00	
	24 V DC/3.1 A, PSU100D		97 x 128 x 38	6EP1332-1LD00	
	24 V DC/4.1 A, PSU100D		97 x 158 x 38	6EP1332-1LD10	
	24 V DC/6.2 A, PSU100D		97 x 178 x 38	6EP1333-1LD00	
	24 V DC/12.5 A, PSU100D		105 x 199 x 41	6EP1334-1LD00	
	24 V DC/5 A, PSU100P	120 – 230 V AC (85 ... 132 V/170 ... 264 V AC)	120 x 181 x 60	6EP1333-7CA00	<ul style="list-style-type: none"> Rugged metal enclosure in IP67 degree of protection for distributed use Signaling contact and LED for operation status
	24 V DC/8 A, ET200pro PS		310 x 135 x 90	6ES7148-4PC00-0HA0	
	48 V DC/5 A, PSU100E	120/230 V AC (85 ... 132/170 - 264 V AC)	42 x 125 x 125	6EP3344-0SB00-0AY0	Single-phase 48 V DC power supply in slim aluminum enclosure
	24 V DC/5 A, PSU300E	400 – 500 V 3 AC (320 ... 550 V 3 AC)	42 x 125 x 125	6EP1433-0AA00	3-phase 24 V DC power supply in a slim aluminium housing
	12 V DC/20 A, PSU3800	400 – 500 V 3 AC (320 ... 575 V 3 AC)	70 x 125 x 125	6EP3424-8UB00-0AY0	<ul style="list-style-type: none"> Optimized power supply for battery charging; with selectable output characteristic, functional expansion possible using expansion modules
	24 V DC/17 A, PSU3800		70 x 125 x 125	6EP3436-8UB00-0AY0	
	24 V DC/30 A, 40 A, PSU3800	135 x 145 x 150	6EP3437-8UB00-0AY0		
3 ... 52 V DC/10A, SITOP PSU3600 flexi	120 – 230 V AC (85 ... 264 V AC, 88 ... 250 V DC)	42 x 125 x 135	6EP3343-0SA00-0AY0	Compact multi-function power supply unit with flexible setting of the output voltage, also dynamically 0 ... 52 V DC via signal input	
2x 15 V DC/3.5 A, SITOP PSU3600 dual	120 – 230 V AC (85 ... 264 V AC, 88 ... 250 V DC)	42 x 125 x 125	6EP3323-0SA00-0BY0	<ul style="list-style-type: none"> Two outputs, each can be set between 12 and 28 V DC, e.g. for +/- 15 V DC or 2 voltage levels, e.g. 12 V DC and 24 V DC Each output with limited power according to NEC Class 2 	

Expansion modules to increase system availability					
	Redundancy module, RED1200	12 V, 24 V, 48 V DC (10 ... 58 V DC)	35 x 135 x 125	6EP4346-7R800-0AX0	<ul style="list-style-type: none"> Redundancy modules RED1200/PSE202U for decoupling SITOP power supply units of the same type: <ul style="list-style-type: none"> 24 V/10 A: 2 power supply units up to 5 A or 1 up to 10 A 24 V/NEC Class 2: 2 up to 40 A with limiting of output to 100 VA 20 A: 2 up to 10 A or 1 up to 20 A 40 A: 2 up to 20 A or 1 up to 40 A Redundancy modules RED1200 additionally provide: <ul style="list-style-type: none"> Decoupling of 12 V to 48 V DC power supply units Series connection to increase the voltage up to 96 V DC Parallel connection of more than 2 power supply units to increase the power In PSU6200 design, push-in terminals Bridges power failures for up to a period of seconds Selectivity modules for electronic protection of 24 V DC feeders and quick fault localization SEL1200: switch-off characteristic for standard protection SEL1400/PSE200U: current-limiting for increased requirements regarding protection Manual activation and deactivation of feeders via reset button Remote reset for temporary faults Sequential connection reduces total inrush current With group signaling contact or single-channel signaling for channel-specific evaluation via SIMATIC S7 function block SEL1200/1400 with diagnostics of voltage, current, set threshold value, reason for shutdown, etc. per output PSE200U: Voltage measuring point for current per output (1 V ≙ 1 A)
	• 20 A		45 x 135 x 125	6EP4347-7R800-0AX0	
	Redundancy module PSE202U	24 V DC (19 ... 29 V DC)	30 x 80 x 100	6EP1964-2BA00	
	• 24 V DC/10 A	24 V DC (19 ... 29 V DC)	30 x 80 x 100	6EP1962-2BA00	
	• 24 V DC/NEC Class2				
	• 24 V DC/40 A	24 V DC (24 ... 28.8 V DC)	70 x 125 x 125	6EP1961-3BA21	
	Buffer module PSE201U 200 ms/ 40 A for SITOP PSU8200, PSU6200 and SITOP smart	24 V DC (24 ... 28.8 V DC)	70 x 125 x 125	6EP1961-3BA01	
	Selectivity module SEL1200	24 V DC (20.4 ... 30 V DC)	45 x 135 x 125	6EP4437-7FB00-3CX0	
	• 4x 2...10 A				
	• 8x 1...5 A	24 V DC (20.4 ... 30 V DC)	45 x 135 x 125	6EP4437-7FB00-3DX0	
	• 8x 2 ... 10 A	24 V DC (20.4 ... 30 V DC)	45 x 135 x 125	6EP4438-7FB00-3DX0	
	Selectivity module SEL1400	24 V DC (20.4 ... 30 V DC)	45 x 135 x 125	6EP4437-7EB00-3CX0	
	• 4x 2 ... 10 A				
	• 8x 1 ... 5 A	24 V DC (20.4 ... 30 V DC)	45 x 135 x 125	6EP4437-7EB00-3DX0	
• 8x 2 ... 10 A	24 V DC (20.4 ... 30 V DC)	45 x 135 x 125	6EP4438-7EB00-3DX0		
Selectivity module PSE200U ... with common alarm signal	24 V DC (22 ... 30 V DC)	72 x 80 x 72	6EP1961-2BA11		
• 4x 0.5 ... 3 A					
• 4x 0.5 ... 3 A NEC Class 2				6EP1961-2BA51	
• 4x 3 ... 10 A				6EP1961-2BA21	
... with single-channel signaling	24 V DC (22 ... 30 V DC)	72 x 80 x 72	6EP1961-2BA31		
• 4x 0.5 ... 3 A					
• 4x 0.5 ... 3 A NEC Class 2				6EP1961-2BA61	
• 4x 3 ... 10 A				6EP1961-2BA41	
Diagnosis module SITOP select	24 V DC (22 ... 30 V DC)	72 x 90 x 90	6EP1961-2BA00		
• 4x 2 ... 10 A					

Maintenance-free SITOP DC UPS with capacitors – Uninterruptible power supply up to minutes					
	24 V DC/15 A, 2.5 kW, UPS500S	24 V DC (22 ... 29 V DC), SITOP 24 V	120 x 125 x 125	6EP1933-2EC41	<ul style="list-style-type: none"> DC UPS modules with integral energy buffer, digital inputs and outputs and USB interface Totally maintenance-free DC UPS with double-layer capacitors SITOP UPS500S can be combined with up to 3 expansion modules UPS501S Capacitors eliminate battery replacement Long service life even at high ambient temperature No ventilation of the mounting location is necessary SITOP-Manager (free download) supports further processing and response of the PC
	24 V DC/15 A, 5 kW, UPS500S		120 x 125 x 125	6EP1933-2EC51	
	24 V DC/15 A, 5 kW, UPS501S	24 V DC, UPS500S	70 x 125 x 125	6EP1935-5PG01	

DC UPS with battery modules – Uninterruptible power supply up to hours, optionally with Ethernet/PROFINET connection and TIA integration					
	SITOP UPS1600, 24 V DC/10 A	24 V DC (22 ... 29 V DC), input voltage via 24 V DC SITOP power supply unit	50 x 125 x 125	6EP4134-3AB00-0AY0	<ul style="list-style-type: none"> DC UPS module with digital inputs/outputs, with USB or Ethernet/Profinet interfaces as option Maintenance-free UPS1100 battery modules with automatic detection by UPS1600 UPS 1100 5 Ah in Lithium technology (LiFePo) with a long durability at high temperature Intelligent battery management for monitoring operational readiness, battery supply line and battery charge status. Selection of optimum, temperature-driven charging characteristic High overload capacity and high charging current Minimum standby consumption SITOP Manager (free SW download) supports configuration and monitoring in PC-based systems Complete integration into TIA: User-friendly engineering in the TIA Portal, function blocks for S7 user programs and WinCC faceplates (free download) Integrated Web server and OPC UA server
	• with USB interface		50 x 125 x 125	6EP4134-3AB00-1AY0	
	• with Ethernet/PROFINET interface (2 ports)		50 x 125 x 125	6EP4134-3AB00-2AY0	
	SITOP UPS1600, 24 V DC/20 A		50 x 125 x 125	6EP4136-3AB00-0AY0	
	• with USB interface		50 x 125 x 125	6EP4136-3AB00-1AY0	
	• with Ethernet/PROFINET interface (2 ports)		50 x 125 x 125	6EP4136-3AB00-2AY0	
	SITOP UPS1600, 24 V DC/40 A	70 x 125 x 150	6EP4137-3AB00-0AY0		
	• with USB interface		6EP4137-3AB00-1AY0		
	• with Ethernet/PROFINET interface (2 ports)		6EP4137-3AB00-2AY0		
	SITOP UPS1100	End-of-charge voltage, automatically set by UPS1600: Battery modules UPS1100 1.2/2.5/3.2/7/12 Ah: 28.0 ... 27.3 V DC (< +20 °C), 26.8 ... 26.3 V DC (> +20 °C) Battery module UPS1100 5 Ah LiFePo: 28.8 V DC (-20 ... +50 °C)	89 x 130 x 107	6EP4131-0GB00-0AY0	
	• 24 V DC/1.2 Ah		190 x 169 x 80	6EP4133-0GB00-0AY0	
	• 24 V DC/3.2 Ah		186 x 186 x 110	6EP4134-0GB00-0AY0	
	• 24 V DC/7 Ah		253 x 186 x 110	6EP4135-0GB00-0AY0	
	• 24 V DC/12 Ah		265 x 115 x 76	6EP4132-0GB00-0AY0	
• 24 V DC/2.5 Ah, extended temperature range	189 x 186 x 113	6EP4133-0JB00-0AY0			
• 24 V DC/5 Ah, LiFePo					

¹⁾ Current ordering data plus terms and conditions of sale and delivery can be found in the Catalog KT10.1 and in the Internet at www.siemens.com/industrymall

Get more information

Subject to changes and errors. The information provided in this brochure contains descriptions or performance characteristics which, in case of actual use, do not always apply as described or which may change as a result of further development of the products. The desired performance characteristics are only binding if expressly agreed in the contract. Availability and technical specifications are subject to change without notice.

All product designations may be trademarks or product names of Siemens AG or supplier companies, the use of which by third parties for their own purposes may violate the rights of the owners.

<https://www.siemens.com/industrymall>

Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, systems, machines and networks. It is necessary to implement a holistic, state-of-the-art industrial security concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial security measures that may be implemented, please visit <https://www.siemens.com/industrymall>

Published by
Siemens AG
Digital Industries
Process Automation
Sillier Rheindürkens, 50
76187 Karlsruhe, Germany

For the U.S., published by
Siemens Industry Inc.
100 Technology Drive
Alpharetta, GA 30005
United States

© Siemens 2020
Printed in Germany
W3 03200.0
Dispo 10001
Article No.: DIPA-T10098-01-7600

SITOP Power Supply

SITOP Power Supply

Top integration. Top efficiency. Top reliability.

siemens.com/sitop

Order overview

Edition 04/2020

Order overview SITOP

Regulated Power Supplies, Expansion modules and DC UPS

	Output/Type	Rated input voltage (range)	Dimensions in mm (WxHxD)	Article No. Siemens ¹⁾	Short description				
Advanced power supplies									
SITOP PSU8600 – The power supply system for digitalization and Industry 4.0									
	PSU8600 1AC basic unit • 24 V DC/20 A/4 x 5 A NEW	100 – 240 V AC/110 – 220 V DC (85...275 V AC/99...275 V DC)	125 x 125 x 150	6EP3336-8MB00-2CY0	<ul style="list-style-type: none"> Compact basic units with 1 or 4 outputs, each overload monitored Expandable without wiring effort: Up to 4 CNX8600 modules and 2 BUF8600/UPS8600 modules Expansion module for up to 36 outputs CNX8600 8x2.5 A with NEC Class 2 Outputs individually adjustable: Voltage (4 - 28 V DC) and current Buffer modules with electrolytic or double-layer capacitors to protect against brief power UPS module with lead or lithium iron phosphate battery modules to protect against longer power failures Two Ethernet/PROFINET ports for optimum integration in plants Integrated Web server and OPC UA server Simple engineering and comprehensive monitoring and diagnosis in TIA Portal Support of energy management due to capturing energy data and selectively switching off the outputs 				
	PSU8600 3AC basic unit • 24 V DC/20 A • 24 V DC/20 A/4 x 5 A • 24 V DC/40 A • 24 V DC/40A/4 x 10 A	400-500 V 3 AC, (320 ... 575 V 3 AC)	80 x 125 x 150 100 x 125 x 150 125 x 125 x 150 125 x 125 x 150	6EP3436-8SB00-2AY0 6EP3436-8MB00-2CY0 6EP3437-8SB00-2AY0 6EP3437-8MB00-2CY0					
	Modular system: CNX8600 expansion module • 24 V DC/4 x 5 A • 24 V DC/4 x 10 A • 24 V DC/8 x 2.5 A NEC Class2	Supply from basic unit PSU8600 via connection „System Clip Link“	60 x 125 x 150 60 x 125 x 150 100 x 125 x 150	6EP4436-8XB00-0CY0 6EP4437-8XB00-0CY0 6EP4436-8XB00-0DY0					
	BUF8600 buffer module • 100 ms/40 A • 300 ms/40 A • 4 s/40 A • 10 s/40 A		60 x 125 x 150 125 x 125 x 150 60 x 125 x 150 125 x 125 x 150	6EP4297-8HB00-0XY0 6EP4297-8HB10-0XY0 6EP4293-8HB00-0XY0 6EP4295-8HB00-0XY0					
	UPS components • UPS module UPS860 • Battery module BAT8600 Pb • Battery module BAT8600 LiFePO4		Energy exchange with UPS8600	60 x 125 x 150 322 x 187 x 110 322 x 187 x 110		6EP4197-8AB00-0XY0 6EP4145-8GB00-0XY0 6EP4143-8JB00-0XY0			
	SITOP PSU8200 – Technology power supply for demanding solutions								
		24 V DC/5 A, PSU8200 24 V DC/10 A, PSU8200 24 V DC/5 A, PSU200M 24 V DC/10 A, PSU200M 24 V DC/20 A, PSU8200	120/230 V AC (85 ... 132/176 ... 264 V AC) 120 – 230/230 – 500 V AC (85 ... 264/176 ... 550 V AC) 120/230 V AC (85 ... 275 V AC/88 ... 350 V DC)	45 x 125 x 125 55 x 125 x 125 70 x 125 x 125 70 x 125 x 125 90 x 125 x 125		6EP3333-8SB00-0AY0 6EP3334-8SB00-0AY0 6EP1333-3BA10 6EP1334-3BA10 6EP1336-3BA10	<ul style="list-style-type: none"> Wide-range input Efficiency levels of up to 95% Extra power feature ($1.5 \times I_{rated}$ for 5 s/min for brief operational overload) Power Boost ($3 \times I_{rated}$ for 25 ms) for triggering protective equipment Switchable characteristic curves for parallel operation and short-circuit protection Operation status indicated by 3 LEDs Output voltage adjustable 24 V power supply units expandable with add-on modules and DC UPS 36 V and 48 V versions enable smaller cross-sections of the load supply lines 		
		24 V DC/40 A, PSU8200 24 V DC/20 A, PSU8200 24 V DC/40 A, PSU8200 36 V DC/13 A, PSU8200 48 V DC/10 A, PSU8200 48 V DC/20 A, PSU8200	120/230 V AC (95 ... 132/190 ... 264 V AC) 400 – 500 V 3 AC (320 ... 575 V 3 AC)	145 x 145 x 150 70 x 125 x 125 135 x 145 x 150 70 x 125 x 125 70 x 125 x 125 135 x 145 x 150		6EP3337-8SB00-0AY0 6EP3436-8SB00-0AY0 6EP3437-8SB00-0AY0 6EP3446-8SB10-0AY0 6EP3446-8SB00-0AY0 6EP3447-8SB00-0AY0			
		Standard power supplies							
		SITOP PSU6200 – The all-rounder power supply for a wide variety of applications							
		12 V DC/2 A, PSU6200 24 V DC/1.3 A, PSU6200 24 V DC/2.5 A, PSU6200	120 – 230 V AC/120 – 240 V DC (85 ... 264 V AC/110 ... 275 V DC)	25 x 100 x 88 25 x 100 x 88 40 x 100 x 88	6EP3321-7SB00-0AX0 6EP3331-7SB00-0AX0 6EP3332-7SB00-0AX0	<ul style="list-style-type: none"> Robust wide range input AC and DC, 3-phase devices also applicable for continuous operation with 2 phases Space-saving, narrow design High efficiency up to 96% High overload capacity thanks to Extra-Power ($1.5 \times I_{nom}$ for 5 s) and constant current behavior Permanent overload capacity ($1.2 \times I_{nom}$) up to 45 °C ambient temperature Push-in terminals for fast connection From 3.7 A: LED and signaling contact "DC OK" From 24 V/10 A and 48 V/5 A: Diagnostics monitor for overload and service life via LEDs Diagnostics interface signals all the relevant device and operating data. Active PFC for low reactive current component Expandable with all SITOP add-on modules 			
		12 V DC/7 A, PSU6200 24 V DC/3.7 A, NEC Class2, PSU6200 24 V DC/5 A, PSU6200	120 – 230 V AC/120 – 240 V DC (85 ... 264 V AC/99 ... 275 V DC)	35 x 135 x 125 35 x 135 x 125 35 x 135 x 125	6EP3323-7SB00-0AX0 6EP3333-7LB00-0AX0 6EP3333-7SB00-0AX0				
		12 V DC/12 A, PSU6200 24 V DC/10 A, PSU6200	120 – 230 V AC/110 – 240 V DC (85 ... 264 V AC/85 ... 275 V DC)	45 x 135 x 125 45 x 135 x 125	6EP3324-7SB00-3AX0 6EP3334-7SB00-3AX0				
		48 V DC/5 A, PSU6200 NEW 24 V DC/20 A, PSU6200	400 – 500 V 3 AC (323 ... 576 V 3 AC/450 ... 600 V DC)	45 x 135 x 125 70 x 135 x 125	6EP3344-7SB00-3AX0 6EP3336-7SB00-3AX0				
		24 V DC/5 A, PSU6200 NEW 24 V DC/10 A, PSU6200 NEW 24 V DC/20 A, PSU6200 NEW		35 x 135 x 125 45 x 135 x 155 70 x 135 x 155	6EP3433-7SB00-0AX0 6EP3434-7SB00-3AX0 6EP3436-7SB00-3AX0				
		SITOP smart – Powerful standard power supply							
		12 V DC/7 A, PSU1005 12 V DC/14 A, PSU1005 24 V DC/2.5 A, PSU1005 24 V DC/5 A, PSU1005 24 V DC/10 A, PSU1005 24 V DC/20 A, PSU1005	120/230 V AC (85 ... 132/170 ... 264 V AC)	50 x 125 x 120 70 x 125 x 120 32,5 x 125 x 120 50 x 125 x 120 70 x 125 x 120 115 x 145 x 150	6EP1322-2BA00 6EP1323-2BA00 6EP1332-2BA20 6EP1333-2BA20 6EP1334-2BA20 6EP1336-2BA10		<ul style="list-style-type: none"> Space-saving, slim design PSU1005 with automatic range switch over 120/230 V AC Extra-Power ($1.5 \times I_{rated}$ for 5 s) for brief operational overload Permanent overload capacity ($1.2 \times I_{rated}$) to 45 °C ambient temperature (24 V devices) Green LED and signaling contact „Output voltage OK“ Adjustable output voltage up to 28.0 V DC or 15.5 V DC (12 V devices) Expandable with, redundancy module, selectivity/diagnostics module, buffer module and DC UPS 		
		24 V DC/5 A, PSU3005 24 V DC/10 A, PSU3005 24 V DC/20 A, PSU3005 24 V DC/40 A, PSU3005	400 – 500 V 3 AC (340 ... 550 V 3 AC)	50 x 125 x 120 70 x 125 x 120 90 x 145 x 150 150 x 145 x 150	6EP1433-2BA20 6EP1434-2BA20 6EP1436-2BA10 6EP1437-2BA20				
		Basic power supplies							
		SITOP lite – Cost-effective basic power supply							
		24 V DC/2.5 A, PSU100L 24 V DC/5 A, PSU100L 24 V DC/10 A, PSU100L 24 V DC/20 A, PSU100L	120/230 V AC (93 ... 132/187 ... 264 V AC) 100 - 240 V AC (85 ... 264 V AC/88 ... 370 V DC)	32,5 x 125 x 120 50 x 125 x 120 70 x 125 x 120 110 x 125 x 125	6EP1332-1LB00 6EP1333-1LB00 6EP1334-1LB00 6EP1336-1LB00	<ul style="list-style-type: none"> For industrial applications and basic requirements Narrow width Green LED for "24 V OK" Adjustable output voltage 			
		LOGO!Power 4th generation – Flat power supply for distribution boards in LOGO! 8 design							
			5 V DC/3.0 A 5 V DC/6.3 A 12 V DC/0.9 A 12 V DC/1.9 A 12 V DC/4.5 A 15 V DC/1.9 A 15 V DC/4.0 A 24 V DC/0.6 A 24 V DC/1.3 A 24 V DC/2.5 A 24 V DC/4 A	100 – 240 V AC (85 ... 264 V AC/110 ... 300 V DC)	36 x 90 x 53 54 x 90 x 53 18 x 90 x 53 36 x 90 x 53 54 x 90 x 53 36 x 90 x 53 54 x 90 x 53 18 x 90 x 53 36 x 90 x 53 54 x 90 x 53 72 x 90 x 53			6EP3310-6SB00-0AY0 6EP3311-6SB00-0AY0 6EP3320-6SB00-0AY0 6EP3321-6SB00-0AY0 6EP3322-6SB00-0AY0 6EP3321-6SB10-0AY0 6EP3322-6SB10-0AY0 6EP3330-6SB00-0AY0 6EP3331-6SB00-0AY0 6EP3332-6SB00-0AY0 6EP3333-6SB00-0AY0	<ul style="list-style-type: none"> The 4th generation with even more power in a smaller space: every performance class is 18 mm (1 modular width) narrower New performance class only 18 mm wide Wide-range AC and DC input Voltage measuring point for output current Up to 90% efficiency over entire load range Very low no-load losses of < 0.3% Constant current and power reserve for loads with high inrush currents Flexible rail or wall mounting Green LED for "Output voltage OK" Adjustable output voltage Temperature range -25 ... +70 °C
			Power supply in SIMATIC-Design						
			24 V DC/2.5 A, PM1207 24 V DC/2 A, PS307 24 V DC/5 A, PS307 24 V DC/10 A, PS307	120/230 V AC (85 ... 132/176 ... 264 V AC) 120/230 V AC (85 ... 132/170 ... 264 V AC)	70 x 100 x 75 40 x 125 x 120 60 x 125 x 120 80 x 125 x 120	6EP1332-1SH71 6ES7307-1BA01-0AA0 6ES7307-1EA01-0AA0 6ES7307-1KA02-0AA0		<ul style="list-style-type: none"> Compact Power Module for the S7-1200 with automatic range switchover System and load power supply for the S7-300 in new narrow design with automatic range switchover Load power supply of S7-1500 in slimline design with automatic range switchover and extra power ($1.5 \times I_{rated}$ for 5 s/min) Power supply for SIMATIC ET 200SP distributed I/O, flat design, with automatic range selection, extra power ($1.5 \times I_{rated}$ for 5 s/min), current monitor and plugs for 6 load circuits Power supply in degree of protection IP67 for electronics/sensors and load voltage for the SIMATIC ET200pro 	
			24 V DC/3 A, PM1507 24 V DC/8 A, PM1507 24 V DC/5 A, ET 200SP PS 24 V DC/10 A, ET 200SP PS	120/230 V AC (85 ... 132 V/170 ... 264 V AC) 120/230 V AC (85 ... 132 V/170 ... 264 V AC)	50 x 147 x 135 75 x 147 x 135 160 x 117 x 75 160 x 117 x 75	6EP1332-4BA00 6EP1333-4BA00 6EP7133-6AB00-0BNO 6EP7133-6AE00-0BNO			
	24 V DC/8 A, ET200pro PS		400 – 480 V 3 AC (340 ... 550 V 3 AC)	310 x 135 x 90	6ES7148-4PC00-0HA0				
	DC/DC converter								
			24 V DC/4 A, PSU3400 12 V DC/8 A, PSU3400 12 V DC/15 A, PSU3400 24 V DC/5 A, PSU3400 24 V DC/10 A, PSU3400 24 V DC/3.5 A, NEC Class 2, PSU3400 24 V DC/5 A, PSU3400 24 V DC/10 A, PSU3400 24 V DC/20 A, PSU400M	12 V DC (9 ... 18 V DC) 24 V DC (14 ... 32 V DC) startup from 18 V 48 V DC (28 ... 54 V DC) startup from 36 V 600 V DC (300 ... 900 V DC) startup from 340 V	32 x 100 x 100 32 x 100 x 100 42 x 125 x 120 32 x 100 x 100 42 x 125 x 120 32 x 100 x 100 42 x 125 x 120 42 x 125 x 120 90 x 125 x 125	6EP3133-0TA10-0AY0 6EP3123-0TA00-0AY0 6EP3124-0TA00-0AY0 6EP3133-0TA00-0AY0 6EP3134-0TA00-0AY0 6EP3233-0TA10-0AY0 6EP3233-0TA00-0AY0 6EP3234-0TA00-0AY0 6EP1536-3AA00	<ul style="list-style-type: none"> Stable output voltage from fluctuating DC voltage Ideal for battery-operated applications such as driverless transport vehicles PSU3400 in narrow metal housing, with reverse polarity protection and high efficiency up to 93.5% PSU3400 24 V DC/24 V DC for compensating voltage losses with long cables High input voltage, e.g. for operation at the DC link of drives High efficiency of 95% 		

¹⁾ Current ordering data plus terms and conditions of sale and delivery can be found in the Catalog KT10.1 and in the Internet at www.siemens.com/industrymall