

## Level Measurement

### Continuous level measurement

#### Controllers / HydroRanger 200

##### Overview



HydroRanger 200 is an ultrasonic level controller for up to six pumps and provides control, differential control, and open channel flow monitoring.

##### Benefits

- Monitors wet wells, weirs and flumes
- Digital communications with built-in Modbus RTU via RS 485
- Compatible with SmartLinX communication options or SIMATIC PDM via RS 485
- Single or dual point level monitoring
- 6 relay (standard), 1 or 3 relay (optional)
- Auto False-Echo Suppression for fixed obstruction avoidance
- Anti-grease ring/tide mark buildup
- Differential amplifier transceiver for common mode noise rejection and improved signal-to-noise ratio
- Wall and panel mounting options

##### Application

For water authorities, municipal water, and wastewater plants, HydroRanger 200 is an economical, low-maintenance solution delivering control efficiency and productivity needed to meet today's exacting standards. It offers single point monitoring with all models, and optional dual-point monitoring with 6 relay model. As well, it has digital communications with built-in Modbus RTU via RS 485. The standard 6 relay HydroRanger 200 will monitor open channel flow and features more advanced relay alarming and pump control functions as well as volume conversion. It is compatible with SIMATIC PDM, allowing for PC configuration and setup. Sonic Intelligence advanced echo-processing software provides increased reading reliability. The optional 1 or 3 relay models provide accurate level measurement functions only; these two models do not provide open channel flow, differential level measurement or volume conversion functions.

HydroRanger 200 uses proven continuous ultrasonic echo ranging technology to monitor water and wastewater of any consistency up to 15 m (50 ft) in depth. Achievable resolution is 0.1 % with accuracy to 0.25 % of range. Unlike contacting devices, HydroRanger 200 is immune to problems caused by suspended solids, harsh corrosives, grease or silt in the effluent, reducing downtime.

- Key Applications: wet wells, flumes/weirs, bar screen control

#### Selection and ordering data

	Article No.				
<b>HydroRanger 100/200 Ultrasonic level controller</b> <b>Continuous, non-contact, 15 m (50 ft) range. Monitors level, volume, and open channel flow in liquids, slurries, and solids.</b>	7ML5034-	●	●	●	●
Click on the Article No. for the online configuration in the PIA Life Cycle Portal.					
<b>Mounting</b>					
Wall mount, standard enclosure	1				
Wall mount, 4 entries, 4 M20 cable glands included	2				
Panel mount <sup>1)</sup>	3				
<b>Power supply</b>					
100 ... 230 V AC			A		
12 ... 30 V DC			B		
<b>Number of measurement points</b>					
Single point model, 6 relays				A	
Dual point model, 6 relays				B	
Single point model, level only, 1 relay <sup>2)</sup>				C	
Single point model, level only, 3 relays <sup>2)</sup>				D	
<b>Communication (SmartLinX)</b>					
Without module					0
SmartLinX PROFIBUS DP module					2
SmartLinX DeviceNet module					3
See SmartLinX product on page for more information					
<b>Approvals</b>					
Ordinary Locations/General Purpose (Non-Ex), CE, UKCA, FM, cCSA <sub>US</sub> , UL Listed, RCM, EAC, KC					1
CSA Class I, Div. 2, Groups A, B, C, and D; Class II, Div. 2, Groups F and G; Class III, EAC Ex Ex tc IIIc T75 °C Dc X (for wall mount applications only)					2

<sup>1)</sup> Available with approval option 1 only.

<sup>2)</sup> This model is level control only; no open channel flow, differential level, or volume conversion functions.

Selection and Ordering data	Order code
<b>Further designs</b>	
Please add "-Z" to Article No. and specify Order code(s).	
Stainless steel tag [69 x 50 mm (2.71 x 1.97 inch)]; Measuring-point number/identification (max. 27 characters) specify in plain text	Y15

Spare parts and accessories	Article No.
<b>Operating Instructions</b>	
All literature is available to download for free, in a range of languages, at <a href="http://www.siemens.com/processinstrumentation/documentation">http://www.siemens.com/processinstrumentation/documentation</a>	
<b>Accessories</b>	
Handheld programmer	A5E36563512
Tag, stainless steel, 12 x 45 mm (0.47 x 1.77 inch), one text line, suitable for enclosure	7ML1930-1AC
Sunshield kit, 304 stainless steel	7ML1930-1GA
USB to RS 232 adapter	7ML1930-6AK
SITRANS RD100, loop powered display - see Chapter 7	7ML5741-...
SITRANS RD150, remote digital display for 4 ... 20 mA and HART devices - see Chapter 7	7ML5742-.....
SITRANS RD200, universal input display with Modbus conversion - see Chapter 7	7ML5740-...
SITRANS RD300, dual line display with totalizer and linearization curve and Modbus conversion - see Chapter 7	7ML5744-...
<b>Spare parts</b>	
Power Supply Board (100 ... 230 V AC)	7ML1830-1MD
Power Supply Board (12 ... 30 V DC)	7ML1830-1ME
MultiRanger 100/200/HydroRanger 200 display, non-HMI	7ML1830-1MF

# Level Measurement

## Continuous level measurement

### Controllers / HydroRanger 200

#### Selection and ordering data (continued)

Spare parts and accessories	Article No.
Removable terminal blocks	A5E38824197

#### Technical specifications

HydroRanger 200	
<b>Mode of Operation</b>	
Measuring principle	Ultrasonic level measurement
Measuring range	0.3 ... 15 m (1 ... 50 ft), transducer dependent
Measuring points	1 or 2
<b>Input</b>	
Analog	0 ... 20 mA or 4 ... 20 mA, from alternate device, scalable (6 relay model)
Discrete	10 ... 50 V DC switching level Logical 0 = 0.5 V DC Logical 1 = 10 ... 50 V DC Max. 3 mA
<b>Output</b>	
EchoMax transducer	44 kHz
Ultrasonic transducer	Compatible transducers: ST-H and EchoMax series XPS-10, XPS 15/15F, and XRS-5
Relays <sup>1)</sup>	Rating 5 A at 250 V AC, non-inductive
• Model with 1 relay <sup>2)</sup>	1 SPST Form A
• Model with 3 relays <sup>2)</sup>	2 SPST Form A/1 SPDT Form C
• Model with 6 relays	4 SPST Form A/2 SPDT Form C
mA output	0 ... 20 mA or 4 ... 20 mA
• Max. load	750 Ω, isolated
• Resolution	0.1 % of range
<b>Accuracy</b>	
Error in measurement	0.25 % of range or 6 mm (0.24 inch), whichever is greater
Resolution	0.1 % of measuring range or 2 mm (0.08 inch), whichever is greater <sup>3)</sup>
Temperature compensation	<ul style="list-style-type: none"> <li>-50 ... +150 °C (-58 ... +302 °F)</li> <li>Integral temperature sensor in transducer</li> <li>External TS-3 temperature sensor (optional)</li> <li>Programmable fixed temperature values</li> </ul>
<b>Rated operating conditions</b>	
Installation conditions	
• Location	Indoor / outdoor
• Installation category	II
• Pollution degree	4
Ambient conditions	
• Ambient temperature (enclosure)	-20 ... +50 °C (-4 ... +122 °F)
• Storage temperature	-20 ... +50 °C (-4 ... +122 °F)
<b>Design</b>	
Weight	
• Wall mount	1.37 kg (3.02 lb)
• Panel mount	1.50 kg (3.31 lb)
Material (enclosure)	Polycarbonate
Degree of protection (enclosure)	
• Wall mount	IP65/Type 4X/NEMA 4X
• Panel mount	IP54/Type 3/NEMA 3
Cable	
• Transducer and mA output signal	2-core copper conductor, twisted, shielded, 300 Vrms, 0.82 mm <sup>2</sup> (18 AWG), Belden 8 760 or equivalent is acceptable
• Max. separation between transducer and transceiver	365 m (1 200 ft)

#### Technical specifications (continued)

HydroRanger 200	
<b>Displays and controls</b>	100 x 40 mm (4 x 1.5 inch) multi-block LCD with backlighting
Programming	Programming using handheld programmer or via PC with SIMATIC PDM software
<b>Power supply<sup>4)</sup></b>	
AC version	100 ... 230 V AC ± 15 %, 50/60 Hz, 36 VA (17 W)
DC version	12 ... 30 V DC (20 W)
<b>Certificates and approvals</b>	<ul style="list-style-type: none"> <li>CE, UKCA, RCM, EAC, KC<sup>5)</sup></li> <li>Lloyd's Register of Shipping</li> <li>ABS Type Approval</li> <li>FM, cCSA<sub>US</sub>, UL listed</li> <li>cCSA<sub>US</sub> Class I, Div. 2, Groups A, B, C, D, Class II, Div. 2, Groups F, G, Class III, EAC Ex (wall mount only)</li> <li>MCERTS Class 3 approved for Open Channel Flow</li> </ul>
<b>Communication</b>	<ul style="list-style-type: none"> <li>RS 232 with Modbus RTU or ASCII via RJ-11 connector</li> <li>RS 485 with Modbus RTU or ASCII via terminal blocks</li> <li>Optional: SmartLinX cards for               <ul style="list-style-type: none"> <li>- PROFIBUS DP</li> <li>- DeviceNet</li> </ul> </li> </ul>

<sup>1)</sup> All relays certified for use with equipment that fails in a state at or under the rated maximums of the relays


<sup>2)</sup> This model is level control only; no open channel flow, differential level or volume conversion functions

<sup>3)</sup> Program range is defined as the empty distance to the face of the transducer plus any range extension

<sup>4)</sup> Maximum power consumption is listed


<sup>5)</sup> EMC performance available upon request

#### Dimensional drawings



HydroRanger 200, dimensions in mm (inch)

#### Circuit diagrams



HydroRanger 200 connections