

**SIEMENS**



Motion Control Drives

# SINAMICS S210 Servo Drive System

Catalog  
D 32

Edition  
December  
2017

[siemens.com/drives](http://siemens.com/drives)

## Related catalogs

<p><b>Motion Control Drives</b> D 31.1 SINAMICS Inverters for Single-Axis Drives Built-In Units</p> <p>E86060-K5531-A111-A1-7600</p>		<p><b>Industrial Controls</b> IC 10 SIRIUS</p> <p>PDF (E86060-K1010-A101-A8-7600)</p>	
<p><b>Motion Control Drives</b> D 31.2 SINAMICS Inverters for Single-Axis Drives Distributed Inverters</p> <p>E86060-K5531-A121-A1-7600</p>		<p><b>Industrial Controls</b> IC 10 AO SIRIUS Classic</p> <p>PDF (E86060-K1010-A191-A5-7600)</p>	
<p><b>SINAMICS S120</b> D 21.3 Chassis Format Converter Units Cabinet Modules</p> <p><b>SINAMICS S150</b> Converter Cabinet Units E86060-K5521-A131-A6-7600</p>		<p><b>Low-Voltage Power Distribution and Electrical Installation Technology</b> LV 10 SENTRON • SIVACON • ALPHA Protection, Switching, Measuring and Monitoring Devices, Switchboards and Distribution Systems</p> <p>PDF/print (E86060-K8280-A101-A6-7600)</p>	
<p><b>Motion Control Drives</b> D 21.4 SINAMICS S120 and SIMOTICS</p> <p>E86060-K5521-A141-A1-7600</p>		<p><b>SIMATIC</b> ST 70 Products for Totally Integrated Automation</p> <p>E86060-K4670-A101-B6-7600</p>	
<p><b>SIMOTICS S-1FG1</b> D 41 <b>Servo geared motors</b> Helical, Parallel shaft, Bevel and Helical worm geared motors</p> <p>E86060-K5541-A101-A3-7600</p>		<p><b>SIMATIC HMI / PC-based Automation</b> ST 80/ST PC Human Machine Interface Systems PC-based Automation</p> <p>E86060-K4680-A101-C5-7600</p>	
<p><b>SIMOTICS GP, SD, XP, DP</b> D 81.1 <b>Low-Voltage Motors</b> Type series 1FP1, 1LE1, 1MB1 and 1PC1 Frame sizes 71 to 315 Power range 0.09 to 200 kW E86060-K5581-A111-A9-7600</p>		<p><b>Industrial Communication</b> IK PI SIMATIC NET</p> <p>E86060-K6710-A101-B8-7600</p>	
<p><b>FLENDER Couplings</b> MD 10.1 Standard Couplings</p> <p>E86060-K5710-A111-A5-7600</p>		<p><b>SITRAIN</b> Training for Industry</p> <p><a href="http://www.siemens.com/sitrain">www.siemens.com/sitrain</a></p>	
<p><b>SIMOGEAR</b> MD 50.1 <b>Geared Motors</b> Helical, parallel shaft, bevel, helical worm and worm geared motors</p> <p>E86060-K5250-A111-A5-7600</p>		<p><b>Products for Automation and Drives</b> CA 01 Interactive Catalog Download</p> <p><a href="http://www.siemens.com/ca01download">www.siemens.com/ca01download</a></p>	
<p><b>Motion Control System</b> PM 21 SIMOTION Equipment for Production Machines</p> <p>E86060-K4921-A101-A4-7600</p>		<p><b>Industry Mall</b> Information and Ordering Platform on the Internet:</p> <p><a href="http://www.siemens.com/industrymall">www.siemens.com/industrymall</a></p>	

**SIEMENS**

# SINAMICS S210 Servo Drive System

Motion Control Drives

Catalog D 32 · December 2017

Dear Customer,

We are pleased to present you with the new Catalog D 32 · December 2017. The catalog provides a comprehensive overview of the new SINAMICS S210 servo drive system consisting of a SINAMICS S210 servo converter, a SIMOTICS S-1FK2 servomotor and a matching One Cable Connection (OCC).

The new single-axis AC/AC servo converter system is characterized by high performance and dynamic response for mid-range Motion Control applications.

The products listed in this catalog are also included in the new edition of the Interactive Catalog CA 01 on DVD-ROM and in the Industry Mall. Please contact your local Siemens office for additional information.

Up-to-date information about SINAMICS is available online at

[www.siemens.com/sinamics-s210](http://www.siemens.com/sinamics-s210)

You can access our Interactive Catalog and our Industry Mall online at

[www.siemens.com/industrymall](http://www.siemens.com/industrymall)

Your personal contact is keen to receive your suggestions and recommendations for improvement. You can find your contact in our contact database at

[www.siemens.com/automation-contact](http://www.siemens.com/automation-contact)

We hope that you will often enjoy using Catalog D 32 · December 2017 as a selection and ordering reference document and wish you every success with our products and solutions.

With kind regards,



Achim Peltz  
Vice President  
General Motion Control  
Siemens AG, Digital Factory Division, Motion Control



# SINAMICS S210 Servo Drive System

## Motion Control Drives



### Catalog D 32 · December 2017

Refer to the Industry Mall for current updates of this catalog:

[www.siemens.com/industrymall](http://www.siemens.com/industrymall)

The products contained in this catalog can also be found in the Interactive Catalog CA 01.

Article No.: E86060-D4001-A510-D8-7600

Please contact your local Siemens branch.

### NEW

Click on an Article No. in the catalog PDF to call it up in the Industry Mall and to obtain all the information.

Article No.

6SL3070-0AA00-0AG0  
6SL3072-0AA00-0AG0



Or directly on the Internet, e.g.  
[www.siemens.com/product?6SL3070-0AA00-0AG0](http://www.siemens.com/product?6SL3070-0AA00-0AG0)



The products and systems described in this catalog are manufactured/distributed under application of a certified quality management system in accordance with DIN EN ISO 900. The certificate is recognized by all IQNet countries.

## System overview

1

## SINAMICS S210 servo drive

2

## SIMOTICS S-1FK2 servomotors

3

## MOTION-CONNECT connection systems

4

## Engineering tools

5

## Services and documentation

6

## Appendix

7

# Digital Enterprise

The building blocks that ensure everything works together perfectly in the digital enterprise

Digitalization is already changing all areas of life and existing business models. It is placing greater pressure on industry while at the same time creating new business opportunities. Today, thanks to scalable solutions from Siemens, companies can already become a digital enterprise and ensure their competitiveness.



## Industry faces tremendous challenges



### Reduce time-to-market

Today manufacturers have to bring products to market at an ever-increasing pace despite the growing complexity of these products. In the past, a major manufacturer would push aside a small one, but now it is a fast manufacturer that overtakes a slow one.




### Boost flexibility

Consumers want customized products, but at a price they would pay for a mass-produced item. That only works if production is more flexible than ever before.



### Improve quality

To ensure a high level of quality while meeting legal requirements, companies have to establish closed quality loops and enable the traceability of products.



### Boost efficiency

Today the product itself needs to be sustainable and environmentally friendly, while energy efficiency in production has become a competitive advantage.



### Increase security

Increasing networking escalates the threat to production facilities of cyberattacks. Today more than ever, companies need suitable security measures.



## The digital enterprise has already become a reality

To fully benefit from all the advantages of digitalization, companies first have to achieve complete consistency of their data. Fully digitally integrated business processes, including those of suppliers, can help to create a digital representation of the entire value chain. This requires

- the integration of industrial software and automation,
- expansion of the communication networks,
- security in automation,
- and the use of business-specific industrial services.

## MindSphere

### The cloud-based open IoT operating system from Siemens

With MindSphere, Siemens offers a cost-effective and scalable cloud platform as a service (PaaS) for the development of applications. The platform, designed as an open operating system for the Internet of Things, makes it possible to improve the efficiency of plants by collecting and analyzing large volumes of production data.

## Totally Integrated Automation (TIA)

### Where digitalization becomes reality

Totally Integrated Automation (TIA) ensures the seamless transition from the virtual to the real world. It already encompasses all the necessary conditions for transforming the benefits of digitalization into true added value. The data that will form the digital twin for actual production is generated from a common base.

### Digital Plant

Learn more about the digital enterprise for the process industry  
[www.siemens.com/digitalplant](http://www.siemens.com/digitalplant)

### Digital Enterprise Suite

Learn more about the digital enterprise for the discrete industry  
[www.siemens.com/digital-enterprise-suite](http://www.siemens.com/digital-enterprise-suite)

# Integrated Drive Systems

Faster on the market and in the black with Integrated Drive Systems

SINAMICS is an important element of a Siemens Integrated Drive System, contributing significantly to increased efficiency, productivity, and availability in industrial production processes.


Integrated Drive Systems are Siemens' trendsetting answer to the high degree of complexity that characterizes drive and automation technology today. The world's only true one-stop solution for entire drive systems is characterized in particular by its threefold integration: Horizontal, vertical,

and lifecycle integration ensure that every drive system component fits seamlessly into the whole system, into any automation environment, and even into the entire lifecycle of a plant.

The outcome is an optimal workflow – from engineering all the way to service that entails more productivity, increased efficiency, and better availability. That's how Integrated Drive Systems reduce time to market and time to profit.

## Horizontal integration

**Integrated drive portfolio:** The core elements of a fully integrated drive portfolio are frequency converters, motors, couplings, and gear units. At Siemens, they're all available from a single source. Perfectly integrated, perfectly interacting. For all power and performance classes. As standard solutions or fully customized. No other player in the market can offer a comparable portfolio. Moreover, all Siemens drive components are perfectly matched, so they are optimally interacting.




You can boost the availability of your application or plant to up to

**99%\***

\*e.g., conveyor application

## Vertical integration

Thanks to **vertical integration**, the complete drive train is seamlessly integrated in the entire automation environment – an important prerequisite for production with maximum value added. Integrated Drive Systems are part of Totally Integrated Automation (TIA), which means that they are perfectly embedded into the system architecture of the entire industrial production process. This enables optimal processes through maximum communication and control.




With TIA Portal you can cut your engineering time by up to

**30%**

## Lifecycle integration

**Lifecycle integration** adds the factor of time: Software and service are available for the entire lifecycle of an Integrated Drive System. That way, important optimization potential for maximum productivity, increased efficiency, and highest availability can be leveraged throughout the system's lifecycle – from planning, design, and engineering to operation, maintenance, and all the way even to modernization.

With Integrated Drive Systems, assets become important success factors. They ensure shorter time to market, maximum productivity and efficiency in operation, and shorter time to profit.



With Integrated Drive Systems you can reduce your maintenance costs by up to

**15%**



## System overview




1/2	<b>The SINAMICS drive family</b>
1/6	<b>Drive selection</b>
1/7	<b>SINAMICS S210 servo drive system</b>
1/12	Order overview
1/14	<b>SINAMICS S210 starter kit</b>

# System overview

## The SINAMICS drive family

### Overview

#### Integration in automation



#### Totally Integrated Automation and communication

SINAMICS is an integral component of the Siemens "Totally Integrated Automation" concept. Integrated SINAMICS systems covering configuration, data storage, and communication at automation level ensure low-maintenance solutions with the SIMATIC, SIMOTION and SINUMERIK control systems.

Depending on the application, the appropriate variable frequency drives can be selected and incorporated in the automation concept. With this in mind, the drives are clearly subdivided into their different applications. A wide range of communication options (depending on the drive type) are available for establishing a communication link to the automation system:

- PROFINET
- PROFIBUS
- EtherNet/IP
- Modbus TCP
- Modbus RTU
- AS-Interface
- BACnet MS/TP

#### Applications

SINAMICS is the comprehensive family of drives from Siemens designed for machine and plant engineering applications. SINAMICS offers solutions for all drive tasks:

- Simple pump and fan applications in the process industry
- Demanding single drives in centrifuges, presses, extruders, elevators, as well as conveyor and transport systems
- Drive line-ups in textile, plastic film, and paper machines as well as in rolling mill plants
- Highly dynamic servo drives for machine tools, as well as packaging and printing machines

**Overview** (continued)*SINAMICS as part of the Siemens modular automation system****Innovative, energy-efficient and reliable drive systems and applications as well as services for the entire drive train***

The solutions for drive technology place great emphasis on the highest productivity, energy efficiency and reliability for all torque ranges, performance and voltage classes.

Siemens offers not only the right innovative variable frequency drive for every drive application, but also a wide range of energy-efficient low voltage motors, geared motors, explosion-protected motors and high-voltage motors for combination with SINAMICS.

Furthermore, Siemens supports its customers with global pre-sales and after-sales services, with over 295 service points in 130 countries – and with special services e.g. application consulting or motion control solutions.

***Energy efficiency***Energy management process

Efficient energy management consultancy identifies the energy flows, determines the potential for making savings and implements them with focused activities.

Almost two thirds of the industrial power requirement is from electric motors. This makes it all the more important to use drive technology permitting energy consumption to be reduced effectively even in the configuration phase, and consequently to optimize plant availability and process stability. With SINAMICS, Siemens offers powerful energy efficient solutions which, depending on the application, enable a significant reduction in electricity costs.

## System overview

1

### The SINAMICS drive family

#### Overview (continued)

##### Up to 70 % potential for savings using variable speed operation

SINAMICS enables great potential for savings to be realized by controlling the motor speed. In particular, huge potential savings can be recovered from pumps, fans and compressors which are operated with mechanical throttle and valves. Here, changing to variable-speed drives brings enormous economic advantages. In contrast to mechanical control systems, the power consumption at partial load operation is always immediately adjusted to the demand at that time. So energy is no longer wasted, permitting savings of up to 60 % – in exceptional cases even up to 70 %. Variable-speed drives also offer clear advantages over mechanical control systems when it comes to maintenance and repair. Current spikes when starting up the motor and strong torque surges become things of the past – and the same goes for pressure waves in pipelines, cavitation or vibrations which cause sustainable damage to the plant. Smooth starting and ramp-down relieve the load on the mechanical system, ensuring a significantly longer service life of the entire drive train.

##### Regenerative feedback of braking energy

In conventional drive systems, the energy produced during braking is converted to heat using braking resistors. Energy produced during braking is efficiently recovered to the supply system by versions of SINAMICS G and SINAMICS S drives with regenerative feedback capability and these devices do not therefore need a braking resistor. This permits up to 60 % of the energy requirement to be saved, e.g. in lifting applications. Energy which can be reused at other locations on a machine. Furthermore, this reduced power loss simplifies the cooling of the system, enabling a more compact design.

##### Energy transparency in all configuration phases


Early on, in the configuration phase, the SIZER for Siemens Drives engineering tool provides information on the specific energy requirement. The energy consumption across the entire drive train is visualized and compared with different plant concepts.

##### SINAMICS in combination with energy-saving motors

Engineering integration stretches beyond the SINAMICS drive family to higher-level automation systems, and to a broad spectrum of energy-efficient motors with a wide range of performance classes, which, compared to previous motors, are able to demonstrate up to 10 % greater efficiency.

#### Variants

Depending on the application, the SINAMICS range offers the ideal variant for any drive task.



**Overview** (continued)**Platform concept**

All SINAMICS variants are based on a platform concept. Joint hardware and software components, as well as standardized tools for dimensioning, configuration, and commissioning tasks ensure high-level integration across all components. SINAMICS handles a wide variety of drive tasks with no system gaps. The different SINAMICS variants can be easily combined with each other.













**Quality management according to EN ISO 9001**

SINAMICS conforms to the most exacting quality requirements. Comprehensive quality assurance measures in all development and production processes ensure a consistently high level of quality.

Of course, our quality management system is certified by an independent authority in accordance with EN ISO 9001.

**IDS – Integration at its very best**

The Siemens Integrated Drive Systems (IDS) solution offers perfectly matched drive components with which you can meet your requirements. The drive components reveal their true strengths as an Integrated Drive System over the full range from engineering and commissioning through to operation: Integrated system configuration is performed using the Drive Technology Configurator: Just select a motor and a converter and design them with the SIZER for Siemens Drives engineering tool. The STARTER and SINAMICS Startdrive commissioning tools integrate the motor data and at the same time simplify efficient commissioning. Integrated Drive Systems are incorporated in the TIA Portal – this simplifies engineering, commissioning and diagnostics.

Low voltage										DC voltage	Medium voltage
Basic performance		General performance					High performance			DC applications	Applications with high outputs
											
SINAMICS V20	SINAMICS V90	SINAMICS G120C G120 G120P G120P Cabinet	SINAMICS G110D G120D G110M SIMATIC ET 200pro FC-2	SINAMICS G130 G150	SINAMICS G180	SINAMICS S110	SINAMICS S210	SINAMICS S120 S120M	SINAMICS S150	SINAMICS DCM	SINAMICS GH150 GH180 GM150 SM150 GL150 SL150 SM120CM
0.12 kW to 30 kW	0.05 kW to 7 kW	0.37 kW to 630 kW	0.37 kW to 7.5 kW	75 kW to 2700 kW	2.2 kW to 6600 kW	0.55 kW to 132 kW	0.05 kW to 0.75 kW	0.55 kW to 5700 kW	75 kW to 1200 kW	6 kW to 30 MW	0.15 MW to 85 MW
Pumps, fans, compressors, conveyor belts, mixers, mills, spinning machines, textile machines, refrigerated display counters, fitness equipment, ventilation systems	Handling machines, packaging machines, automatic assembly machines, metal forming machines, printing machines, winding and unwinding units	Pumps, fans, compressors, conveyor belts, mixers, mills, extruders, building management systems, process industry, HVAC, single-axis positioning applications in machine and plant engineering	Conveyor technology, single-axis positioning applications (G120D)	Pumps, fans, compressors, conveyor belts, mixers, mills, extruders	Sector-specific for pumps, fans, compressors, conveyor belts, extruders, mixers, mills, kneaders, centrifuges, separators	Single-axis positioning applications in machine and plant engineering	Packaging machines, handling equipment, feed and withdrawal devices, stacking units, automatic assembly machines, laboratory automation, wood, glass and ceramics industry, digital printing machines	Production machines (packaging, textile and printing machines, paper machines, plastic processing machines), machine tools, plants, process lines and rolling mills, marine drives, test bays	Test bays, cross cutters, centrifuges	Rolling mill drives, wire-drawing machines, extruders and kneaders, cableways and lifts, test bay drives	Pumps, fans, compressors, mixers, extruders, mills, crushers, rolling mills, conveyor technology, excavators, test bays, marine drives, blast furnace fans, retrofit
Catalog D 31.1	Brochure V90	Catalogs D 31.1, D 35	Catalog D 31.2	Catalog D 11	Catalog D 18.1	Catalog D 31.1	Catalog D 32	Catalogs D 21.3, D 21.4 NC 62	Catalog D 21.3	Catalog D 23.1	Catalogs D 15.1, D 12
Engineering tools (e.g. Drive Technology Configurator, SIZER for Siemens Drives, STARTER and SINAMICS Startdrive)											

G\_D011\_EN\_00450j

# System overview

## Drive selection

1

### Overview

#### SINAMICS selection guide – typical applications

Use	Requirements for torque accuracy/speed accuracy/position accuracy/coordination of axes/functionality					
	Continuous motion			Non-continuous motion		
	Basic	Medium	High	Basic	Medium	High
<b>Pumping, ventilating, compressing</b> 	Centrifugal pumps Radial / axial fans Compressors	Centrifugal pumps Radial / axial fans Compressors	Eccentric screw pumps	Hydraulic pumps Metering pumps	Hydraulic pumps Metering pumps	Descaling pumps Hydraulic pumps
	V20 G120C G120P	G120P G130/G150 G180 <sup>1)</sup>	S120	G120	S110	S120
<b>Moving</b> 	Conveyor belts Roller conveyors Chain conveyors	Conveyor belts Roller conveyors Chain conveyors Lifting/lowering devices Elevators Escalators/moving walkways Indoor cranes Marine drives Cable railways	Elevators Container cranes Mining hoists Excavators for open-cast mining Test bays	Acceleration conveyors Storage and retrieval machines	Acceleration conveyors Storage and retrieval machines Cross cutters Reel changers	Storage and retrieval machines Robotics Pick & place Rotary indexing tables Cross cutters Roll feeds Engagers/disengagers
	V20 G110D G110M G120C ET 200pro FC-2 <sup>2)</sup>	G120 G120D G130/G150 G180 <sup>1)</sup>	S120 S150 DCM	V90 G120 G120D	S110 <b>S210</b> DCM	S120 <b>S210</b> DCM
<b>Processing</b> 	Mills Mixers Kneaders Crushers Agitators Centrifuges	Mills Mixers Kneaders Crushers Agitators Centrifuges Extruders Rotary furnaces	Extruders Winders/unwinders Lead/follower drives Calenders Main press drives Printing machines	Tubular bagging machines Single-axis motion control such as • Position profiles • Path profiles	Tubular bagging machines Single-axis motion control such as • Position profiles • Path profiles	Servo presses Rolling mill drives Multi-axis motion control such as • Multi-axis positioning • Cams • Interpolations
	V20 G120C	G120 G130/G150 G180 <sup>1)</sup>	S120 S150 DCM	V90 G120	S110 <b>S210</b>	S120 <b>S210</b> DCM
<b>Machining</b> 	Main drives for • Turning • Milling • Drilling	Main drives for • Drilling • Sawing	Main drives for • Turning • Milling • Drilling • Gear cutting • Grinding	Axis drives for • Turning • Milling • Drilling	Axis drives for • Drilling • Sawing	Axis drives for • Turning • Milling • Drilling • Lasering • Gear cutting • Grinding • Nibbling and punching
	S110	S110 S120	S120	S110	S110 S120	S120

#### Using the SINAMICS selection guide

The varying range of demands on modern variable frequency drives requires a large number of different types. Selecting the optimum drive has become a significantly more complex process. The application matrix shown simplifies this selection process considerably, by suggesting the ideal SINAMICS drive for examples of typical applications and requirements.

- The application type is selected from the vertical column
  - Pumping, ventilating, compressing
  - Moving
  - Processing
  - Machining
- The quality of the motion type is selected from the horizontal row
  - Basic
  - Medium
  - High

#### More information

Further information about SINAMICS is available on the Internet at [www.siemens.com/sinamics](http://www.siemens.com/sinamics)

Practical application examples and descriptions are available on the Internet at [www.siemens.com/sinamics-applications](http://www.siemens.com/sinamics-applications)

<sup>1)</sup> Industry-specific converters.

<sup>2)</sup> Information on the SIMATIC ET 200pro FC-2 frequency converter is available at [www.siemens.com/et200pro-fc](http://www.siemens.com/et200pro-fc)

## Overview



Example: SINAMICS S210 converter, frame size FSB with SIMOTICS S-1FK2 servomotor, shaft height 30

The new servo drive system comprises a SINAMICS S210 servo converter, a SIMOTICS S-1FK2 servomotor and a matching One Cable Connection (OCC) for connecting the motor to the converter. The SINAMICS S210 is a single-axis AC/AC servo converter system with high performance and dynamic response for mid-range Motion Control applications.

SINAMICS S210 servo converters are available for line voltages of 200 ... 240 V 1 AC, and the SIMOTICS S-1FK2 servomotors for a performance range from 0.05 ... 0.75 kW with shaft heights of 20 mm, 30 mm and 40 mm in the High Dynamic (HD) and Compact (CT) versions.

The SINAMICS S210 can be used in numerous applications. Typical applications are:

- Packaging machines
- Handling equipment
- Feed and withdrawal devices
- Stacking units
- Automatic assembly machines
- Laboratory automation
- Woodworking, glass and ceramic industries
- Digital printing machines

### Flexible in application

The SINAMICS S210 is a flexible, versatile system. SINAMICS S-1FK2 series synchronous servomotors are installed in rotary and linear axes. The integrated One Cable Connection (OCC) interface allows user-friendly connection of a SIMOTICS S-1FK2 motor with just one cable. The electronic motor type plate data can be read out, which eliminates the need to parameterize the converter with the motor data. This significantly simplifies and shortens commissioning.

In conjunction with the technological functions of the higher-level controller, there are many possibilities of motion – everything is possible, such as continuous operation, positioning and synchronous operation, and coordinated motion of multiple axes via cyclic cams or interpolation.

The SINAMICS S210 converter has an integrated PROFINET communications interface for connecting to a control system.

The data exchange with the higher-level controllers takes place via standardized protocols – the PROFIdrive profile for positioning mode and the PROFIsafe profile for safety-related communication.

Thus, operation is optimally ensured with the SIMATIC S7 automation system. The drive axis is connected via technology objects and Motion Control blocks in the SIMATIC S7 or a SIMOTION controller.

### High performance for fast and precise control

The high performance of the SINAMICS S210 servo drive system in conjunction with the SIMOTICS S-1FK2 servomotor derives from the following features:

- Low moment of inertia and high overload capability of the motor
- High-resolution encoder with fast scanning
- Current controller clock cycle of 62.5  $\mu$ s and a pulse frequency of 8 kHz of the servo converter

This enables short cycle times on the machine even with complex motion control.


## System overview

### SINAMICS S210 servo drive system

1

#### Overview (continued)

##### Optimized connection technology with One Cable Connection (OCC)



SINAMICS S210 M12 OCC connecting cable

Motor and converter are simply connected to one another by one instead of the usual two or three cables. With this One Cable Technology, energy supply, encoder signals and braking signal are brought together in a single cable. This results in the following advantages:


- Time-saving by laying only one cable
- Smaller installation space and space requirement in cable collars, tight bending radii
- Only one cable has to be cleaned. This is advantageous, e.g. in the pharmaceutical industry and where higher requirements are placed upon hygiene
- Can be ordered to the decimeter
- Motor-side M12 (smallest OCC connector worldwide) and M17 connection plugs
- Rotatable connectors on the motor side
- Motor with very low interfering contour for restricted installation space.

Cables are available in two different qualities:

- MOTION-CONNECT 500
- MOTION-CONNECT 800PLUS

As well as the pre-assembled cable, individual components (connectors and goods sold by the meter) can also be ordered for self assembly.

##### Easy commissioning due to web server and One Button Tuning



One Button Tuning

The web server of the converter offers a simple means of parameter assignment. The web server allows commissioning purely oriented on the functionality of the drive. With the web server, the SINAMICS S210 servo drive system can be brought into operation with a few clicks.

As a result of reading the electronic type plate of the connected SIMOTICS S-1FK2 servomotor, only a few operator actions, such as automatic controller optimization with One Button Tuning, are necessary, as the motor and encoder are automatically detected. The controller parameters are automatically optimized. The three selectable dynamic levels of the controller can optimally take into account the desired behavior of the connected mechanics.

A motion of the axis can take place directly via the control panel during commissioning.

The customer benefits from the web server in many ways:

- Commissioning can also be easily done in places difficult to access, as the web server in the converter can also be accessed directly via PROFINET from the controller.
- The web server provides full diagnostic capability without the need for additional software.
- Commissioning and diagnostics can also be done without a cable via mobile devices, such as laptops, smart phones and tablets (an additional WLAN access point is necessary).
- Intuitive user interface

For more information, see the [Engineering tools section](#).



**Overview** (continued)**Diagnostics**

Faults and warnings are shown on the display located under the front cover, and they can be acknowledged with the Acknowledge button. Extensive diagnostics with plain text messages for cause and remedy information is possible via the web server.

**Safety Integrated**

The integrated safety functions can provide highly effective application-oriented protection for personnel and machinery (terms as defined in IEC 61800-52).

The following Safety Integrated Basic functions are included as standard:

- Safe Torque Off (STO)
- Safe Brake Control (SBC)
- Safe Stop 1 (SS1)

The following Safety Integrated Extended functions <sup>1)</sup> are available as options:

- Safe Stop 2 (SS2)
- Safe Operating Stop (SOS)
- Safely-Limited Speed (SLS)
- Safe Speed Monitor (SSM)
- Safe Direction (SDI)

The Safety Integrated functions are fully integrated into the drive system. They can be activated via fail-safe digital inputs on the converter (only STO and SS1) or via PROFINET with PROFIsafe.

The Safety Integrated functions are implemented electronically and therefore offer short response times in comparison to solutions with externally implemented monitoring functions.

**Perfect combination with SIMATIC S7-1500, SIMATIC S7-1500 T-CPU and PROFINET**

It communicates with the higher-level control via PROFINET IRT. SIMATIC S7-1500, SIMATIC S7-1500 T-CPU and SIMOTION can be used as controllers for the optimal interaction between controller and the SINAMICS S210 servo drive system.

The SINAMICS S210 servo converter has an integrated PROFINET communications interface with a cycle of up to 250 µs for connecting to a control system.

Standardized protocols for linking to a higher-level control with RT and IRT are supported – the PROFIdrive profile with DSC for positioning mode and the PROFIsafe profile for safety-related communication. Functions, such as Shared Device, ring redundancy and PROFInergy, are also possible.

Everything from one source: Through the use of Motion Control functionalities in the controller, the combination of converter and SIMATIC S7 automation system or a SIMOTION controller allows ideally harmonized engineering. As a result, commissioning times are shortened.

Via technology objects and Motion Control blocks of the higher-level controller, there are many possibilities of motion, such as continuous operation, positioning and synchronous operation, and coordinated motion of multiple axes via cyclic cams or interpolation.

Siemens offers tested SIMATIC PLC/HMI application examples for connection of the servo drive system to a SIMATIC controller: [www.siemens.com/sinamics-applications](http://www.siemens.com/sinamics-applications)


Further information about SIMATIC S7-1500 and SIMATIC S7-1500 T-CPU controllers is available in Catalog ST 70 and on the Internet at [www.siemens.com/simatic-s7-1500](http://www.siemens.com/simatic-s7-1500)

<sup>1)</sup> Available soon. The extended functions require safety-capable motors.

## System overview

### SINAMICS S210 servo drive system

#### Overview (continued)




#### Ruggedness

The SINAMICS S210 is equipped as standard with varnished or partially varnished modules. The painting on the modules protects the sensitive SMD components against corrosive gases, chemically active dust and moisture.

#### Can be used worldwide

In addition to the usual approvals, the SINAMICS S210 drive system also has UL approval for the North American market. This means that the drive system, comprising SINAMICS S210 and SIMOTICS S-1FK2, including the One Cable Connection (OCC), can be used worldwide.

Overview (continued)



# System overview

## SINAMICS S210 servo drive system

### Order overview

#### SINAMICS S210 drive system

SIMOTICS S-1FK2 servomotor							SINAMICS S210 servo converter supply voltage 200 ... 240 V 1 AC			MOTION-CONNECT motor connection cable
Static torque	Maximum torque	Maximum speed	Rated power	Rated torque	Rotor moment of inertia	Article No.	Max. motor power	Frame size	Article No.	Article No.
$M_0$	$M_{max}$	$n_{max}$	$P_{rated}$	$M_{rated}$	$J_{Mot}$		$P_{rated}$			
Nm (lb <sub>r</sub> -ft)	Nm (lb <sub>r</sub> -ft)	rpm	kW (hp)	Nm (lb <sub>r</sub> -ft)	kg cm <sup>2</sup> (lb <sub>r</sub> -in <sup>2</sup> )		kW			
<b>High Dynamic for highly dynamic applications</b>							<b>SINAMICS S210 servo converter</b>			<b>One Cable Connection</b>
<b>Shaft height 20 – rated speed <math>n_{rated}</math> 3000 rpm</b>										
0.16 (0.12)	0.56 (0.41)	8000	0.05 (0.07)	0.16 (0.12)	0.0245 (0.008)	<b>1FK2102-0AG</b>	0.1	FSA	<b>6SL3210-5HB10-1UF0</b>	<b>6FX</b>
0.32 (0.24)	1.11 (0.82)	8000	0.1 (0.13)	0.32 (0.24)	0.036 (0.012)	<b>1FK2102-1AG</b>	0.1	FSA	<b>6SL3210-5HB10-1UF0</b>	<b>6FX</b>
<b>Shaft height 30 – rated speed <math>n_{rated}</math> 3000 rpm</b>										
0.64 (0.47)	1.95 (1.44)	8000	0.2 (0.27)	0.64 (0.47)	0.093 (0.032)	<b>1FK2103-2AG</b>	0.2	FSA	<b>6SL3210-5HB10-2UF0</b>	<b>6FX</b>
1.27 (0.94)	4.05 (2.99)	7300	0.4 (0.54)	1.27 (0.94)	0.139 (0.047)	<b>1FK2103-4AG</b>	0.4	FSB	<b>6SL3210-5HB10-4UF0</b>	<b>6FX</b>
<b>Shaft height 40 – rated speed <math>n_{rated}</math> 3000 rpm</b>										
1.27 (0.94)	3.85 (2.84)	7400	0.4 (0.54)	1.27 (0.94)	0.35 (0.120)	<b>1FK2104-4AK</b>	0.4	FSB	<b>6SL3210-5HB10-4UF0</b>	<b>6FX</b>
2.4 (1.77)	7.6 (5.61)	7100	0.75 (1.01)	2.4 (1.77)	0.56 (0.191)	<b>1FK2104-5AK</b>	0.75	FSC	<b>6SL3210-5HB10-8UF0</b>	<b>6FX</b>
<b>Compact for high precision applications</b>							<b>SINAMICS S210 servo converter</b>			<b>One Cable Connection</b>
<b>Shaft height 30 – rated speed <math>n_{rated}</math> 3000 rpm</b>										
0.64 (0.47)	1.85 (1.36)	8000	0.2 (0.27)	0.64 (0.47)	0.2 (0.068)	<b>1FK2203-2AG</b>	0.2	FSA	<b>6SL3210-5HB10-2UF0</b>	<b>6FX</b>
1.27 (0.94)	3.75 (2.77)	7800	0.4 (0.54)	1.27 (0.94)	0.35 (0.120)	<b>1FK2203-4AG</b>	0.4	FSB	<b>6SL3210-5HB10-4UF0</b>	<b>6FX</b>
<b>Article No. supplements</b>										
<b>Holding brake</b>										
Without brake										0
With brake										1
<b>Degree of protection</b>										
IP64 (without shaft sealing ring)										0
IP65 (with shaft sealing ring)										1
<b>Shaft extension, feather key</b>										
Plain shaft										0
Shaft with feather key										1
Plain shaft $\varnothing 11 \times 23$ mm (0.43 $\times$ 0.91 in) (only for 1FK2 . 03 and IP64)										0 2
<b>Encoder</b>										
AS20DQC (absolute encoder 20-bit singleturn)										C
AM20DQC (absolute encoder 20-bit + 12-bit multiturn)										D
<b>Pre-assembled MOTION-CONNECT cable</b>										
MOTION-CONNECT 500										5
MOTION-CONNECT 800PLUS										8
<b>Length code (max. 50 m (164 ft))</b>										
0 m (0 ft)										A
10 m (32.8 ft)										B
20 m (65.6 ft)										C
30 m (98.4 ft)										D
40 m (131 ft)										E
50 m (164 ft)										F
0 m (0 ft)										A
1 m (3.28 ft)										B
2 m (6.56 ft)										C
3 m (9.84 ft)										D
4 m (13.1 ft)										E
5 m (16.4 ft)										F
6 m (19.7 ft)										G
7 m (23.0 ft)										H
8 m (26.2 ft)										J
9 m (29.5 ft)										K
0 m (0 ft)										0
0.1 m (0.33 ft)										1
0.2 m (0.66 ft)										2
0.3 m (0.98 ft)										3
0.4 m (1.31 ft)										4
0.5 m (1.64 ft)										5
0.6 m (1.97 ft)										6
0.7 m (2.30 ft)										7
0.8 m (2.62 ft)										8

## Order overview (continued)

## Accessories for SINAMICS S210 servo converters

Description	Article No.
<b>SINAMICS SD card (optional)</b> 512 MB The parameter assignment, firmware and licenses for a converter can be stored on this memory card	
• Empty	<b>6SL3054-4AG00-2AA0</b>
• With firmware V5.1	<b>6SL3054-4FB00-2BA0</b>
<b>PROFINET patch cable</b> For the networking of concatenated converters	
• 0.3 m (0.98 ft)	<b>6XV1870-3QE30</b>
• 0.5 m (1.64 ft)	<b>6XV1870-3QE50</b>
<b>Line filter (optional) <sup>1)</sup></b> European standard EN 61008-3 Category C2 can also be achieved for cable lengths up to 25 m (82 ft) with this line filter. Category C3 is reached with cable lengths up to 50 m (164 ft).	<b>6SL3203-0BB21-8VA0</b>

## Accessories for SIMOTICS S-1FK2 servomotors

Description	For motor	Article No.
<b>Shaft sealing ring (optional)</b> To achieve degree of protection IP65 for retrofitting or as spare part	1FK2 . 02	<b>1FK2902-0GC00</b>
	1FK2 . 03	<b>1FK2903-0GC00</b>
	1FK2 . 04	<b>1FK2904-0GC00</b>

## Accessories for MOTION-CONNECT connection systems

## OCC extension cables

Description	For motor	Article No. (See table on page 1/12 for length codes)
<b>Pre-assembled OCC extension cable MOTION-CONNECT 500</b>	1FK2102 and 1FK2 . 03	<b>6FX5002-8QE04-1■■■■</b>
	1FK2104	<b>6FX5002-8QE08-1■■■■</b>
<b>Pre-assembled OCC extension cable MOTION-CONNECT 800PLUS</b>	1FK2102 and 1FK2 . 03	<b>6FX8002-8QE04-1■■■■</b>
	1FK2104	<b>6FX8002-8QE08-1■■■■</b>
<b>Pre-assembled OCC extension cable MOTION-CONNECT 500</b> With connector supplied on the converter side <sup>2)</sup>	1FK2102 and 1FK2 . 03	<b>6FX5012-8QE04-1■■■■</b>
	1FK2104	<b>6FX5012-8QE08-1■■■■</b>
<b>Pre-assembled OCC extension cable MOTION-CONNECT 800PLUS</b> With connector supplied on the converter side <sup>2)</sup>	1FK2102 and 1FK2 . 03	<b>6FX8012-8QE04-1■■■■</b>
	1FK2104	<b>6FX8012-8QE08-1■■■■</b>

## OCC components for self assembly

Description	For motor	Article No. (See table on page 1/12 for length codes)
<b>Sold by the meter OCC line MOTION-CONNECT 500 <sup>2)</sup></b>	1FK2102 and 1FK2 . 03	<b>6FX5008-1BE04-1■■■■</b>
	1FK2104	<b>6FX5008-1BE08-1■■■■</b>
<b>Sold by the meter OCC line MOTION-CONNECT 800PLUS <sup>2)</sup></b>	1FK2102 and 1FK2 . 03	<b>6FX8008-1BE04-1■■■■</b>
	1FK2104	<b>6FX8008-1BE08-1■■■■</b>
<b>Motor-side M12 SPEED-CONNECT connector <sup>2)</sup></b>	1FK2102 and 1FK2 . 03	<b>6FX2003-0LU64</b>
<b>Motor-side M17 SPEED-CONNECT connector <sup>2)</sup></b>	1FK2104	<b>6FX2003-0LU54</b>
<b>M12 SPEED-CONNECT connector with external thread for extension cable <sup>2)</sup></b>	1FK2102 and 1FK2 . 03	<b>6FX2003-0LA64</b>
<b>M17 SPEED-CONNECT connector with external thread for extension cable <sup>2)</sup></b>	1FK2104	<b>6FX2003-0LA54</b>
<b>Converter-side Siemens IX signal connector <sup>2)</sup></b>	–	<b>6FX2003-0DE01</b>
<b>Shield clamp</b> (Packing unit: 10 items)	–	<b>6FX2003-7EX10</b>

## Control cabinet bushings

Description	For motor	Article No.
<b>Mounting flange</b>	1FK2102 and 1FK2 . 03	<b>6FX2003-7JX00</b>
	1FK2104	<b>6FX2003-7HX00</b>

## Recommended SIMATIC S7 controller

Further information about SIMATIC S7-1500 and SIMATIC S7-1500 T-CPU controllers is available in Catalog ST 70 and on the Internet at [www.siemens.com/simatic-s7-1500](http://www.siemens.com/simatic-s7-1500)

<sup>1)</sup> The line filter does not have UL approval.

<sup>2)</sup> Available soon.

## System overview

### SINAMICS S210 starter kit

1

#### Overview



The SINAMICS S210 starter kit with Article No. 6SL3200-0AE60-0AA0 comprises

- a SINAMICS S210 servo converter, 230 V 1 AC, 400 W (Article No. 6SL3210-5HB10-4UF0)
- a SIMOTICS S-1FK2 servomotor, High Dynamic, shaft height 30, 400 W, without brake, shaft with feather key, with absolute encoder 20-bit singleturn + 12-bit multiturn (Article No. 1FK2103-4AG00-1DA0)
- a corresponding One Cable Connection cable (OCC), 3 m (Article No. 6FX5002-8QN04-1AD0)

The delivery quantity is limited to three per customer.

The SINAMICS S210 starter kit can be perfectly combined with the SIMATIC S7-1500 starter kit. In this way, Motion Control applications can be quickly and easily implemented.

Further information about the SIMATIC starter kit, see: [www.siemens.com/s7-1500-starterkits](http://www.siemens.com/s7-1500-starterkits)

#### Selection and ordering data

Description	Article No.
<b>SINAMICS S210 starter kit</b> With SINAMICS S210 servo converter, SIMOTICS S-1FK2 servomotor and OCC line (3 m (9.84 ft)), power rating 400 W	<b>6SL3200-0AE60-0AA0</b>

## SINAMICS S210 servo drive



<b>2/2</b>	<b>SINAMICS S210 servo drive</b>
2/2	Overview
2/3	Design
2/4	Function
2/4	Configuration
2/5	Integration
2/6	Selection and ordering data
2/7	Technical specifications
2/9	Dimensional drawings
2/9	Accessories
<b>2/10</b>	<b>Line-side components</b>
2/10	Line filters
2/10	Recommended line-side overcurrent protective devices
<b>2/11</b>	<b>DC link components</b>
2/11	External braking resistors
<b>2/12</b>	<b>Supplementary system components</b>
2/12	Memory cards

## SINAMICS S210 servo drive

0.1 kW to 0.75 kW

### SINAMICS S210 servo drive

#### Overview

**SINAMICS S210 – the single-axis servo drive for highly dynamic applications**



SINAMICS S210 frame sizes FSA to FSC

The SINAMICS S210 servo converter is designed for connection to SIMOTICS S-1FK2 synchronous servomotors.

PROFINET RT/IRT is available for connection to a higher-level control system. That allows, above all, SIMATIC S7 and SIMOTION to be used as controllers.

SINAMICS S210 is optimized for operation with SIMATIC S7-1500 and SIMATIC S7-1500T, which have their own positioning functionality. Therefore no additional basic positioner is integrated into the converter.

The converter works with a servo controller with or without Dynamic Servo Control (DSC) and has a torque setpoint limitation. A wide range of internal protection functions are included to protect the converter.

The status of the converter is indicated by two multi-color LEDs and a 7-segment display. Pending faults can be acknowledged with a button under the front cover.

The converter has a web server, which can be called via the service interface or via PROFINET from a web browser on a PC. Both commissioning and diagnostics can be performed through this. With the web server, the converter can be brought into operation in a few steps. As the motor data from the converter is read from the electronic type plate, they do not need to be parameterized. The PROFIdrive telegram is automatically accepted by the controller; so only the controller parameters have to be adjusted. This is simply done with the One Button Tuning function, which automatically determines the parameters.

SIMOTICS S-1FK2 servomotors can be connected and operated via a One Cable Connection (OCC) line. Third-party motors cannot be connected because the converter requires the type plate data of the motor.

No additional components are required for controlling the motor holding brake as all the required components are integrated into the converter.

The converter can be operated optionally with a memory card. The card is inserted in the card slot behind the front cover. Firmware and drive parameters can be stored on the memory card, so that the converter can easily be replaced without any other aids. This memory card can also be used to perform series commissioning on multiple drives of identical type.

The card is available as an empty memory card or containing the latest drive firmware version. The memory card also contains the licenses for chargeable functions, such as the safety license for the Extended Safety functions. To use these functions, a memory card containing the corresponding safety license must be permanently inserted.


If necessary, the converter contains an integrated braking resistor. As a result of the generous dimensioning of the resistor and the DC link capacities, an external braking resistor is only necessary to meet very high requirements.

The converter also has an integrated line filter that fulfills category C2 up to a cable length of 10 m and category C3 up to 25 m.

With an optional line filter, cable lengths up to 25 m are also possible with category C2 and up to 50 m with category C3.



## Overview (continued)



2

## Design

The single-axis AC/AC converter contains a power unit and a Control Unit for the powerful communication, open and closed-loop control functions.

The SINAMICS S210 servo converter features the following connections and interfaces as standard:

- Fieldbus interface
  - 1 PROFINET interface with two ports (RJ45 sockets) with PROFIdrive V4 profile
- 1 service interface for Ethernet communications with a service PC
- One Cable Connection (OCC)
  - 1 communications connector for communication with the encoder of the SIMOTICS S-1FK2 motor
  - 1 motor power connector for the power conductors of the SIMOTICS S-1FK2 motor
  - 1 brake connection for the conductors of the motor holding brake of the SIMOTICS S-1FK2 motor
- 1 connection for the electronic power supply via the 24 V DC supply connector (supply can be looped through connectors for several SINAMICS S210)
- 1 connection for the line voltage and an external braking resistor (optional)
- Digital inputs
  - 1 fail-safe digital input (isolated) for controlling STO and SS1 via terminals
  - 2 high-speed digital inputs for measuring probe or reference marks
  - 1 digital input for monitoring the temperature of an external braking resistor
- 1 slot for a memory card on which the firmware, parameters and licenses can be stored
- 1 display with 3-digit, 7-segment display for indicating faults and two status LEDs
- 1 button for acknowledging errors

## SINAMICS S210 servo drive

0.1 kW to 0.75 kW

### SINAMICS S210 servo drive

#### Function

<b>Closed-loop control</b>	Servo control with DSC
<b>Control functions</b>	Speed control with encoder Dynamic Servo Control (DSC) Torque setpoint limitation Current controller and current controller adaptation suitably adjusted for SIMOTICS S-1FK2 servomotors One Button Tuning with moment of inertia estimator and reference model Local measuring probe Simple brake control Direction reversal without changing the setpoint channel Travel to fixed stop Vertical axis Speed controller adaptation Thermal monitoring for power unit and servomotor
<b>Protective functions</b>	Undervoltage DC link voltage Overvoltage DC link voltage Overcurrent power unit Overcurrent motor Overload power unit ( $I^2t$ ) Short-circuit Ground fault Temperature rise servomotor Temperature rise power unit
<b>Safety Integrated</b>	Safe Torque Off (STO) Safe Brake Control (SBC) Safe Stop 1 (SS1) Safe Stop 2 (SS2) <sup>1)</sup> Safe Operating Stop (SOS) <sup>1)</sup> Safely Limited Speed (SLS) <sup>1)</sup> Safe Speed Monitor (SSM) <sup>1)</sup> Safe Direction (SDI) <sup>1)</sup>
<b>Commissioning</b>	Identification of the SIMOTICS S-1FK2 motors via the electronic type plate Automatic controller optimization

#### Configuration

The following electronic configuring aids and engineering tools are available for the SINAMICS S210 servo converters:

##### **Drive Technology Configurator (DT Configurator) within the CA 01**

The Interactive Catalog CA 01 – the offline Industry Mall of Siemens on DVD-ROM – contains over 100000 products with approximately 5 million possible drive system product variants. The Drive Technology Configurator (DT Configurator) has been developed to facilitate selection of the correct motor and/or converter from the wide spectrum of drives. It is integrated as a selection tool in Catalog CA 01.

##### **Online DT Configurator**

In addition, the DT Configurator can be used on the Internet without requiring any installation. The DT Configurator can be found in the Siemens Industry Mall at the following address:  
[www.siemens.com/dt-configurator](http://www.siemens.com/dt-configurator)

##### **SIZER for Siemens Drives engineering tool (available soon for SINAMICS S210)**

The PC-based SIZER for Siemens Drives engineering tool makes it easy to engineer the SINAMICS drive family. It provides support when selecting the hardware and firmware components necessary to implement a drive task. SIZER for Siemens Drives supports the complete configuration of the drive system, from basic single drives to demanding multi-axis applications.

The SIZER for Siemens Drives engineering tool is available free on the Internet at  
[www.siemens.com/sizer](http://www.siemens.com/sizer)

##### **SINAMICS web server for SINAMICS S210**

The converter can be brought easily and quickly into operation and optimized with the web server. Additional software does not need to be installed as access comes directly from a web browser.

You can find further information about the web server for SINAMICS S210 in the Engineering tools section.

##### **SINAMICS Startdrive commissioning tool (available soon for SINAMICS S210)**

SINAMICS Startdrive is a tool for configuring, commissioning, and diagnosing the SINAMICS family of drives that is integrated into the TIA Portal.


The SINAMICS Startdrive has been optimized with regard to user friendliness and consistent use of the TIA Portal benefits of a common working environment for PLC, HMI and drives.

The SINAMICS Startdrive commissioning tool is available free on the Internet at  
[www.siemens.com/startdrive](http://www.siemens.com/startdrive)

<sup>1)</sup> Available soon. The extended functions require safety-capable motors.

**Integration**

2





Connection example SINAMICS S210 servo converter




**SINAMICS S210 servo drive**

0.1 kW to 0.75 kW

**SINAMICS S210 servo drive****Selection and ordering data**

Description	Frame size	Article No.
<b>200 ... 240 V 1 AC</b>		
<b>SINAMICS S210 servo converters</b> Incl. shield plate and push-in connector without memory card		
	• 0.1 kW FSA	<b>6SL3210-5HB10-1UF0</b>
	• 0.2 kW FSA	<b>6SL3210-5HB10-2UF0</b>
	• 0.4 kW FSB	<b>6SL3210-5HB10-4UF0</b>
	• 0.75 kW FSC	<b>6SL3210-5HB10-8UF0</b>

**Accessories**

Description	Article No.
 <p><b>SINAMICS SD card (optional)</b> 512 MB</p> <p>The parameter assignment, firmware and licenses for a converter can be stored on this memory card</p> <ul style="list-style-type: none"> <li>• Empty</li> <li>• With firmware V5.1</li> </ul>	<p><b>6SL3054-4AG00-2AA0</b></p> <p><b>6SL3054-4FB00-2BA0</b></p>
 <p><b>PROFINET patch cable</b> For the networking of concatenated converters Industrial Ethernet TP cord, CAT 6 A, twisted pair line 4 × 2 cores, pre-assembled with two RJ45 connectors</p> <ul style="list-style-type: none"> <li>• 0.3 m (0.98 ft)</li> <li>• 0.5 m (1.64 ft)</li> </ul>	<p><b>6XV1870-3QE30</b></p> <p><b>6XV1870-3QE50</b></p>
 <p><b>Line filter (optional) <sup>1)</sup></b> European standard EN 61008-3 Category C2 can also be achieved for cable lengths up to 25 m (82 ft) with this line filter. Category C3 is reached with cable lengths up to 50 m (164 ft).</p>	<b>6SL3203-0BB21-8VA0</b>
<p><b>Replacement connector set 230 V 1 AC</b> For frame sizes FSA, FSB and FSC with a set of connectors, as in scope of supply and two shield plates</p>	<b>6SL3260-2DB00-0AA0</b>

<sup>1)</sup> The line filter does not have UL approval.

## Technical specifications

Unless explicitly specified otherwise, the following technical specifications are valid for all SINAMICS S210 servo converters.

### General technical specifications

#### Mechanical specifications

##### Vibratory load

- Transport <sup>1)</sup> acc. to EN 60721-3-2
- Operation acc. to EN 60721-3-3
  - Test values according to EN 60068-2-6

Class 2M3  
 Class 3M2  
 Test Fc (sinusoidal)

- 10 ... 13 Hz: 0.075 mm amplitude of deflection
- 13 Hz ... 150 Hz: 1 × g acceleration amplitude
- 10 frequency cycles per axis

##### Shock load

- Transport <sup>1)</sup> acc. to EN 60721-3-2
- Operation acc. to EN 60721-3-3
  - Test values according to EN 60068-2-27

Class 2M3  
 Class 3M2  
 Test Ea (semisinusoidal)

- 5 × g peak acceleration
- 30 ms duration
- 3 shocks in all three axes in both directions

#### Environmental conditions

##### Protection class

According to EN 61800-5-1

Class I (with protective bonding circuit) and class III (PELV or SELV)

##### Degree of protection

According to EN 60529

IP20  
 Mounting in control cabinet necessary

##### Permissible ambient temperature (air) in operation

0 ... 50 °C (32 ... 122 °F)

##### Installation altitude

Up to max. 4000 m (13123 ft)

- Up to 1000 m (3281 ft) above sea level without derating
- As from 1000 m (3281 ft) derating 10 % of current or 5 K per 1000 m (3281 ft)
- Isolation transformer required as from 2000 m (6562 ft)

##### Climatic environmental conditions

- Storage <sup>2)</sup> acc. to EN 60721-3-1
- Transport <sup>1)</sup> acc. to EN 60721-3-2
- Operation acc. to EN 60721-3-3

Class 1K4  
 -25 ... +55 °C (-13 ... +131 °F)

Class 2K4  
 -40 ... +70 °C (-40 ... +158 °F)  
 Max. air humidity: 95 % at 40 °C (104 °F)

Better than class 3K3  
 0 ... 50 °C (32 ... 122 °F)  
 Relative air humidity: 5 ... 95 %  
 Condensation, splashwater, and ice formation not permitted (EN 60204, Part 1)

##### Environmental class/harmful chemical substances

- Storage <sup>2)</sup> acc. to EN 60721-3-1
- Transport <sup>1)</sup> acc. to EN 60721-3-2
- Operation acc. to EN 60721-3-3

Class 1C2  
 Class 2C2  
 Class 3C2

##### Organic/biological influences

- Storage <sup>2)</sup> acc. to EN 60721-3-1
- Transport <sup>1)</sup> acc. to EN 60721-3-2
- Operation acc. to EN 60721-3-3

Class 1B2  
 Class 2B2  
 Class 3B2

##### Degree of pollution

According to EN 61800-5-1

2

#### Standards

##### Certificates of suitability

CE, cULus, RCM, EAC

<sup>1)</sup> In transport packaging.

<sup>2)</sup> In product packaging.

# SINAMICS S210 servo drive

0.1 kW to 0.75 kW

## SINAMICS S210 servo drive


### Technical specifications (continued)

Line voltage 200 ... 240 V 1 AC		SINAMICS S210 servo converters			
		6SL3210-5HB10-1UF0	6SL3210-5HB10-2UF0	6SL3210-5HB10-4UF0	6SL3210-5HB10-8UF0
<b>Line supply connection</b>					
• Supply voltage		200 ... 240 V ±10 % 1 AC			
• Line frequency	Hz	50/60			
• Conductor cross-section, max.	mm <sup>2</sup>	2.5			
<b>Rated current</b>	A	1.4	2.7	5	9.3
<b>Inrush current</b>	A	8	8	8	8
<b>Power loss</b>	W	15.7	23.2	38.5	71.1
<b>Electronic power supply</b>					
• Voltage		24 V -15 % ... +20 %			
• Power requirement, max.	A	1.6			
• Conductor cross-section, max.	mm <sup>2</sup>	2.5			
<b>Output</b>					
• Rated power for motor	kW	0.1	0.2	0.4	0.75
• Rated current for motor	A	0.8	1.36	2.4	4.4
• Output current for motor, max.	A	3.1	4.8	8.7	16
<b>Pulse frequency power unit</b>	kHz	8			
<b>Output frequency</b>	Hz	0 ... 550			
<b>Line filter</b>		Integrated, category C2 (up to 10 m (32.8 ft) cable length)			
<b>Braking resistor</b>		Without <sup>1)</sup>	Integrated	Integrated	Integrated
<b>Digital inputs <sup>2)</sup></b>					
• Fast inputs for measuring probes, reference marks, temperature monitoring, external braking resistor		3			
- Low level		-30 V ... +5 V and ≤2 mA			
- High level		15 V ... 30 V			
- Current consumption	mA	6			
- Delay time, typ. L → H	µs	5			
- Delay time, typ. H → L	µs	50			
- Galvanic isolation		No			
• Fail-safe input		1			
- Low level		-30 V ... +5 V and ≤2 mA			
- High level		15 V ... 30 V			
- Current consumption	mA	5			
- Delay time, typ. L → H	µs	50			
- Delay time, typ. H → L	µs	100			
- Galvanic isolation		Yes			
• Conductor cross-section, max.	mm <sup>2</sup>	1.5			
<b>Cooling</b>		Convection (without fan)			
<b>Frame size</b>		FSA	FSA	FSB	FSC
<b>Dimensions</b>					
• Width	mm (in)	45 (1.77)	45 (1.77)	55 (2.17)	70 (2.76)
• Height	mm (in)	170 (6.69)	170 (6.69)	170 (6.69)	170 (6.69)
• Depth	mm (in)	170 (6.69)	170 (6.69)	170 (6.69)	195 (7.68)
<b>Weight, approx.</b>	kg (lb)	1.1 (2.43)	1.1 (2.43)	1.2 (2.65)	1.9 (4.19)


<sup>1)</sup> An internal braking resistor is not required for normal operation on account of the available DC link capacity.

<sup>2)</sup> The specified delay times refer to the hardware. The actual reaction time depends on the time slot in which the digital input is processed.


## Dimensional drawings



Dimension drawing, frame size FSA



Dimension drawing, frame size FSB



Dimension drawing, frame size FSC

All dimensions in mm (values in brackets are in inches).

With the OCC motor connection cable connected, the overall depth increases by 56.6 mm (2.28 inches).

## Accessories

### Line filters

Filters are already integrated in order to achieve category C2 (for motor cable lengths up to 10 m) or category C3 (for motor cable lengths up to 25 m). Further requirements can be achieved using an external line filter.

	Maximum motor cable length	
	for converters without additional line filter	for converters with external line filter
EMC category C2	10 m (32.8 ft)	25 m (82 ft)
EMC category C3	25 m (82 ft)	50 m (164 ft)

### Recommended line-side overcurrent protective devices

Overcurrent protective devices are absolutely necessary for the operation of the converters. The table listed in the section "Recommended line-side overcurrent protective devices" provides recommendations according to IEC and UL regulations, depending on the area of application. Recommendations on further overcurrent protective devices are available at: <https://support.industry.siemens.com/cs/document/109748999>

Additional information about the listed Siemens fuses is available in Catalog LV 10 as well as in the Industry Mall.

### Braking resistors

As far as necessary, braking resistors are integrated into the converters. Together with the generously dimensioned DC link capacities, an external braking resistor is not necessary in the normal case.

If the internal braking resistor is inadequate for applications with very high requirements, an external braking resistor can be connected as an alternative.

### Memory cards

A memory card (SINAMICS SD card) can be optionally used with SINAMICS S210. The associated slot is located under the front cover of the converter. Not only the firmware but also the device parameterization of a SINAMICS S210 servo converter can be stored on the memory card.

When service is required, e.g. after the converter has been replaced and the data have been downloaded from the memory card, the drive system is immediately ready for use again.

A memory card is only absolutely necessary, if functions requiring license, such as the Extended Safety functions, are used. The necessary license is saved on the memory card.

**SINAMICS S210 servo drive**

0.1 kW to 0.75 kW

**Line-side components > Line filters****Technical specifications**

Line voltage 200 ... 240 V 1 AC		Line filter <sup>1)</sup>
		6SL3203-0BB21-8VA0
<b>Rated current</b>	A	18
<b>Line/load connection</b>		Screw terminals
• Conductor cross-section	mm <sup>2</sup>	10
<b>PE connection</b>		M5 screw stud
<b>Degree of protection</b>		IP20
<b>Dimensions</b>		
• Width	mm (in)	59 (2.32)
• Height	mm (in)	153 (6.02)
• Depth	mm (in)	55 (2.17)
<b>Weight, approx.</b>	kg (lb)	0.9 (1.98)
<b>Suitable for SINAMICS S210 servo converters</b>	Type	6SL3210-5HB10-1UF0 (0.1 kW) 6SL3210-5HB10-2UF0 (0.2 kW) 6SL3210-5HB10-4UF0 (0.4 kW) 6SL3210-5HB10-8UF0 (0.75 kW)

**Selection and ordering data**

Rated power of the servo converter	Suitable for SINAMICS S210	Line filter <sup>1)</sup>
kW		Article No.
<b>Line voltage 200 ... 240 V 1 AC</b>		
0.1	6SL3210-5HB10-1UF0	<b>6SL3203-0BB21-8VA0</b>
0.2	6SL3210-5HB10-2UF0	
0.4	6SL3210-5HB10-4UF0	
0.75	6SL3210-5HB10-8UF0	

**Line-side components > Recommended line-side overcurrent protective devices****Selection and ordering data**

Overcurrent protective devices are absolutely necessary for the operation of the converters. The following table lists recommendations for fuses.

- Siemens fuses of type 3NA3 for use in the area of validity of IEC
- UL-listed fuses Class J for use in USA and Canada

Recommendations on further overcurrent protective devices are available at:

<https://support.industry.siemens.com/cs/document/109748999>

The Short Circuit Current Rating (SCCR) according to UL for industrial control cabinet installations to NEC Article 409 or UL 508A/508C or UL 61800-5-1 is as follows for Class J fuses for

- SINAMICS S210: 65 kA

SCCR and ICC values for combination with further overcurrent protective devices are available at:

<https://support.industry.siemens.com/cs/document/109748999>

Notes for installations in Canada:

The converters are intended for line supply systems with over-voltage category III.

More information is available in the technical documentation on the Internet at:

[www.siemens.com/sinamics-s210/documentation](http://www.siemens.com/sinamics-s210/documentation)

Additional information about the listed Siemens fuses is available in Catalog LV 10 as well as in the Industry Mall.

Rated power	SINAMICS S210	IEC-compliant		UL/cUL-compliant	
		Fuse		Fuse type	
kW	Type 6SL3210-...	Current	<b>3NA3</b>	Rated voltage 600 V AC	Current
		A	Article No.	Class	A
<b>Line voltage 200 ... 240 V 1 AC</b>					
0.1	5HB10-1UF0	6	<b>3NA3801</b>	J	6
0.2	5HB10-2UF0	6	<b>3NA3801</b>	J	6
0.4	5HB10-4UF0	10	<b>3NA3803</b>	J	10
0.75	5HB10-8UF0	16	<b>3NA3805</b>	J	20

<sup>1)</sup> The line filter does not have UL approval.



## Overview

As far as necessary, braking resistors are integrated into the converters. Together with the generously dimensioned DC link capacities, another external braking resistor is not necessary in the normal case.

If the internal braking resistor is inadequate for applications with very high requirements, an external braking resistor can be connected as an alternative.

Only intrinsically safe braking resistors with temperature monitoring may be used in order to minimize the risk of an explosion, the outbreak of fire or melting of the enclosure in the event of a continuous overload, e.g. due to a defect.

## Technical specifications

### Requirements placed on an external braking resistor

External braking resistor				
Frame size of servo converter	Resistance	Rated power	Max. power	Max. energy
Frame size	$\Omega$	W	kW	kJ
<b>200 ... 240 V 1 AC</b>				
FSA	150	20	1.09	0.8
FSB	100	21	1.64	1.23
FSC	50	62	3.28	2.46

## More information

Further information is available from the "Siemens Product Partner for Drives Options":

[www.siemens.com/drives-options-partner](http://www.siemens.com/drives-options-partner)

**SINAMICS S210 servo drive**

0.1 kW to 0.75 kW

Supplementary system components &gt; Memory cards

**Overview**

SINAMICS memory card (SD card)

The parameter assignment, firmware and licenses for a converter can be stored on the SINAMICS memory card (SD card). When service is required, e.g. after the converter has been replaced and the data have been downloaded from the memory card the drive system is immediately ready for use again.

The memory card has the following functions:

- Parameter settings can be written from the memory card to the converter or saved from the converter to the memory card
- The memory card supports series commissioning without the use of a commissioning tool
- If firmware is stored on the memory card, the firmware can be upgraded/downgraded during startup
- It is used for storing licenses when using functions requiring license

Note:


In general, the converter can be operated without a memory card. However, it is necessary if licenses, such as the Extended Safety license, are required. The card must then remain permanently inserted.

**Selection and ordering data**

Description	Article No.
<b>SINAMICS SD card</b> 512 MB	
• Empty	<b>6SL3054-4AG00-2AA0</b>
• With firmware V5.1	<b>6SL3054-4FB00-2BA0</b>

2

## SIMOTICS S-1FK2 servomotors




<b>3/2</b>	<b>SIMOTICS S-1FK2 servomotors for SINAMICS S210</b>
3/2	Overview
3/2	Benefits
3/2	Application
3/3	Selection and ordering data
3/5	Technical specifications
3/5	General technical specifications
3/10	SIMOTICS S-1FK2 shaft height 20
3/12	SIMOTICS S-1FK2 shaft height 30
3/14	SIMOTICS S-1FK2 shaft height 40

## SIMOTICS S-1FK2 servomotors

### SIMOTICS S-1FK2 servomotors for SINAMICS S210

#### Overview



The SIMOTICS S-1FK2 servomotors are compact and highly dynamic synchronous motors for a wide range of uses in an industrial environment. They are characterized by high power density, degree of protection and overload capability.

#### **SIMOTICS S-1FK2 High Dynamic motors**

Highest dynamic response through low inertia for highly dynamic applications with low moved masses.

#### **SIMOTICS S-1FK2 Compact motors**

Precise, stable control with medium to high masses to be moved with medium moment of inertia.

#### Benefits

The SIMOTICS S-1FK2 servomotors fully exploit their strengths in the system with the SINAMICS S210 converter:

- Short adjustment and positioning times
- Quick and precise compensation of disturbances
- Stable closed loop control with high dynamic response









This is achieved by:

- Rapid control cycle
- High pulse frequency
- Complex rule algorithms
- High-resolution optical encoder with fast scanning
- Low moment of inertia of the motors
- High overload capability

#### Application

- Packaging machines
- Handling equipment
- Feed and withdrawal devices
- Stacking units
- Automatic assembly machines
- Laboratory automation
- Woodworking, glass and ceramic industries
- Digital printing machines

## Selection and ordering data

	Static torque $M_0$ Nm (lb <sub>f</sub> -ft)	Maximum torque $M_{max}$ Nm (lb <sub>f</sub> -ft)	Maximum speed $n_{max}$ rpm	Rated power $P_{rated}$ kW (hp)	Rated torque $M_{rated}$ Nm (lb <sub>f</sub> -ft)	Rotor moment of inertia $J_{Mot}$ kg cm <sup>2</sup> (lb <sub>f</sub> -in <sup>2</sup> )	SIMOTICS S-1FK2 servomotor Article No.
<b>High Dynamic for highly dynamic applications</b>							
<b>Shaft height 20 – rated speed <math>n_{rated}</math> 3000 rpm</b>							
	0.16 (0.12)	0.56 (0.41)	8000	0.05 (0.07)	0.16 (0.12)	0.0245 (0.008)	<b>1FK2102-0AG</b> ■■■-■■■A0
	0.32 (0.24)	1.11 (0.82)	8000	0.1 (0.13)	0.32 (0.24)	0.036 (0.012)	<b>1FK2102-1AG</b> ■■■-■■■A0
<b>Shaft height 30 – rated speed <math>n_{rated}</math> 3000 rpm</b>							
	0.64 (0.47)	1.95 (1.44)	8000	0.2 (0.27)	0.64 (0.47)	0.093 (0.032)	<b>1FK2103-2AG</b> ■■■-■■■A0
	1.27 (0.94)	4.05 (2.99)	7300	0.4 (0.54)	1.27 (0.94)	0.139 (0.047)	<b>1FK2103-4AG</b> ■■■-■■■A0
<b>Shaft height 40 – rated speed <math>n_{rated}</math> 3000 rpm</b>							
	1.27 (0.94)	3.85 (2.84)	7400	0.4 (0.54)	1.27 (0.94)	0.35 (0.120)	<b>1FK2104-4AK</b> ■■■-■■■A0
	2.4 (1.77)	7.6 (5.61)	7100	0.75 (1.01)	2.4 (1.77)	0.56 (0.191)	<b>1FK2104-5AK</b> ■■■-■■■A0
<b>Compact for high precision applications</b>							
<b>Shaft height 30 – rated speed <math>n_{rated}</math> 3000 rpm</b>							
	0.64 (0.47)	1.85 (1.36)	8000	0.2 (0.27)	0.64 (0.47)	0.2 (0.068)	<b>1FK2203-2AG</b> ■■■-■■■A0
	1.27 (0.94)	3.75 (2.77)	7800	0.4 (0.54)	1.27 (0.94)	0.35 (0.120)	<b>1FK2203-4AG</b> ■■■-■■■A0

## Article No. supplements

<b>Holding brake</b>			
Without brake		0	
With brake		1	
<b>Degree of protection</b>			
IP64 (without shaft sealing ring)		0	
IP65 (with shaft sealing ring)		1	
<b>Shaft extension, feather key</b>			
Plain shaft		0	
Shaft with feather key		1	
Plain shaft $\varnothing 11 \times 23$ mm (0.43 $\times$ 0.91 in) (only for 1FK2 . 03 and IP64)		0 2	
<b>Encoder</b>			
Absolute encoder 20-bit singleturn			C
Absolute encoder 20-bit singleturn + 12-bit multiturn			D

## Accessories

Version	Description	For motor	Article No.
	<b>Shaft sealing ring</b>	1FK2 . 02	<b>1FK2902-0GC00</b>
	To achieve degree of protection IP65	1FK2 . 03	<b>1FK2903-0GC00</b>
	Degree of protection kit for mounting on the motor for retrofitting or as spare part	1FK2 . 04	<b>1FK2904-0GC00</b>

## SIMOTICS S-1FK2 servomotors

## SIMOTICS S-1FK2 servomotors for SINAMICS S210

## Selection and ordering data (continued)

## Structure of the Article No. of the SIMOTICS S-1FK2 servomotors

Data position in Article No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16		
	1	F	K	2	■	■	■	-	■	A	■	■	■	-	■	■	A	0
<u>1st to 4th position:</u> digit, letter, letter, digit	<b>Motor</b>	1	F	K	2													
<u>5th position:</u> digit	<b>Moment of inertia</b>																	
	High Dynamic				1													
	Compact				2													
<u>6th and 7th positions:</u> digit, digit	<b>Shaft height</b>																	
	20					0	2											
	30					0	3											
	40					0	4											
<u>8th position:</u> digit	<b>Overall length</b>																	
	See specific technical specifications							0 ... 8										
<u>9th position:</u> letter	Reserved								A									
<u>10th position:</u> letter	<b>Winding/rated speed</b>																	
	<b>For converters connected to max. 240 V</b>																	
	3000 rpm at 230 V																	G
	1500 rpm at 230 V																	F
	3000 rpm at 230 V																	K
<u>11th position:</u> digit	<b>Brake</b>																	
	None																	0
	Holding brake																	1
<u>12th position:</u> digit	<b>Degree of protection</b>																	
	IP64 (without shaft sealing ring)																	0
	IP65 (with shaft sealing ring)																	1
<u>13th position:</u> digit	<b>Shaft extension, feather key</b>																	
	Plain shaft Ø 14 × 30 mm (0.55 × 1.18 in)																	0
	Shaft with feather key Ø 14 × 30 mm (0.55 × 1.18 in)																	1
	Plain shaft Ø 11 × 23 mm (0.43 × 0.91 in) (only for 1FK2 . 03 and IP64)																	2
<u>14th position:</u> letter	<b>Encoder</b>																	
	Absolute encoder 20-bit singleturn (AS20DQC)																	C
	Absolute encoder 20-bit + 12-bit multiturn (AM20DQC)																	D
<u>15th position:</u> letter	<b>One Cable Connection</b>																	A
<u>16th position:</u> digit	Reserved																	0

## Technical specifications

### General technical specifications

SIMOTICS S-1FK2 High Dynamic/Compact motors	
<b>Motor type</b>	Permanent-magnet synchronous motor
<b>Permissible operating conditions without derating</b>	
• Ambient temperature	-15 ... +40 °C (5 ... 104 °F)
• Installation altitude, max.	1000 m (3281 ft)
<b>Degree of protection</b> According to EN 60034-5 (IEC 60034-5)	IP64 IP65 optional or retrofittable
<b>Cooling</b> According to EN 60034-6	Natural cooling (IC410)
<b>Type of construction</b> According to EN 60034-7 (IEC 60034-7)	IM B5 (IM V1, IM V3)
<b>Shaft extension</b> According to DIN 748-3 (IEC 60072-1)	Plain shaft Optional shaft with feather key (half-key balancing)
<b>Shaft and flange accuracy</b> According to DIN 42955 (IEC 60072-1)	Tolerance N In each case for radial eccentricity of the shaft extension, concentricity of the centering ring, and axial eccentricity of the mounting flange to the axis of the shaft extension.
<b>Vibration severity grade</b> According to EN 60034-14 (IEC 60034-14)	Grade A is maintained up to rated speed
<b>Stator winding insulation</b> According to EN 60034-1 (IEC 60034-1)	
• 1FK2 . 02, 1FK2 . 03	Thermal class 130 (B) for a winding overtemperature of $\Delta T = 80$ K
• 1FK2 . 04	Thermal class 155 (F) for a winding overtemperature of $\Delta T = 100$ K
<b>Sound pressure level <math>L_{pA}</math> (1 m), max.</b> According to ISO 1680	55 dB
<b>Encoder system</b>	<ul style="list-style-type: none"> <li>AS20DQC (absolute encoder 20-bit singleturn)</li> <li>AM20DQC (absolute encoder 20-bit + 12-bit multiturn)</li> </ul>
<b>Holding brake</b>	Optionally integrated holding brake (zero-backlash, 24 V DC)
<b>Connection</b>	One Cable Connection (OCC) for signals and power Rotatable connector
<b>Paint finish</b>	RAL 7016 (anthracite gray)
<b>Certificates of suitability</b>	cURus, CE

## SIMOTICS S-1FK2 servomotors

### SIMOTICS S-1FK2 servomotors for SINAMICS S210

#### Technical specifications (continued)

##### Regulations, standards, specifications

The motors comply with the appropriate standards and regulations, see table below.

As a result of the fact that in many countries the national regulations have been completely harmonized with the international IEC 60034-1 recommendation, there are no longer any differences with respect to coolant temperatures, temperature classes and temperature rise limits.

General specifications for rotating electrical machines	IEC 60034-1
Terminal designations and direction of rotation for electrical machines	IEC 60034-8
Types of construction of rotating electrical machines	IEC 60034-7
Cooling methods of rotating electrical machines	IEC 60034-6
Degrees of protection of rotating electrical machines	IEC 60034-5
Vibration severity of rotating electrical machines	IEC 60034-14
Noise limit values for rotating electrical machines	IEC 60034-9
Cylindrical shaft extensions for electrical machines	DIN 748-3/IEC 60072-1



SIMOTICS S-1FK2 motors have UL approval from Underwriters Laboratories Inc. and are marked with the "UL Recognized Component" test symbol. This is used for components which are part of a larger product or system. This confirmed compliance with the corresponding US American and Canadian regulations, and allowed access to the North American market.



For SIMOTICS S-1FK2 motors, conformity with the relevant EC directives 2006/95/EC and 2014/35/EU and the relevant standards EN 60034-1:2010 and EN 60204-1:2006 is confirmed. By applying the CE mark to the product, Siemens AG confirms this for the product, and secures the free movement of goods within the European Union.

##### Degree of protection acc. to IEC 60034-5

A suitable degree of protection must be selected according to the operating and environmental conditions to protect the machine against damage caused by the ingress of water and other liquids, as well as dust and foreign bodies.

SIMOTICS S-1FK2 motors have degree of protection IP64 as standard.

The motor can be optionally supplied with a radial shaft seal ring in degree of protection IP65. This increases the protection against the ingress of liquids.

The degree of protection designation is composed of the code **IP** (for International Protection) and two code numbers for the protection against touching and penetration of foreign bodies, and the degree of protection against the ingress of water.

##### First code number

6: Protection against dust ingress and complete protection against touching

##### Second code number

4: Protection against splashwater from all directions

5: Protection against jet water from any direction

##### Recommended degrees of protection for AC motors

When cooling lubricants are used, protection against water alone is inadequate. The IP rating should only be considered as a guide value in this case. The motors may have to be protected by suitable covers. Attention must be paid to providing suitable sealing of the motor shaft for the selected degree of protection for the motor.




The following table can serve as a decision aid for selecting the proper degree of protection for motors. A permanent covering of liquid on the flange must be avoided when the motor is mounted with the shaft extension facing upwards (IM V3).

Effect	General workshop environment	Water/ general cooling lubricant (95 % water, 5 % oil)
Dry	IP64	–
Water-enriched environment	–	IP64
Mist	–	IP65
Spray	–	IP65



**Technical specifications** (continued)**Type of construction, mounting position according to IEC 60034-7**

SIMOTICS S-1FK2 motors are designed in type of construction IM B5. It can also be used in mounting positions IM V1 and IM V3.

Code 1	IM B5	IM V1	IM V3
Code 2	IM 3001	IM 3011	IM 3031
	 Horizontal flange mounting	 Flange mounting, output shaft pointing vertically downwards	 Flange mounting, output shaft pointing vertically upwards

**Shaft and flange accuracy in accordance with IEC 60072-1**




Radial eccentricity tolerance of shaft in relation to housing axis  
(Referred to the cylindrical shaft extension)

Motor	Shaft height	Shaft extension D × L mm (in)	Radial eccentricity, tolerance N μm
1FK2 . 02	20	8 × 25 (0.31 × 0.98)	≤30
1FK2 . 03	30	11 × 23 (0.43 × 0.91) 14 × 30 (0.55 × 1.18)	≤35
1FK2 . 04	40	19 × 40 (0.75 × 1.57)	≤40

Concentricity and axial eccentricity tolerance of the flange  
surface for the shaft axis

(Referred to the centering diameter of the mounting flange)

Motor	Shaft height	Centering diameter mm (in)	Concentricity and axial eccentricity tolerance N μm
1FK2 . 02	20	30 (1.18)	≤80
1FK2 . 03	30	50 (1.97)	≤80
1FK2 . 04	40	70 (2.76)	≤80

**Test: radial eccentricity****Test: concentricity****Test: axial eccentricity**

## SIMOTICS S-1FK2 servomotors


### SIMOTICS S-1FK2 servomotors for SINAMICS S210

#### Technical specifications (continued)

##### Vibration severity and vibration severity grade A according to IEC 60034-14

The vibration severity is the RMS value of the vibration velocity (frequency range from 10 Hz to 1000 Hz). The vibration severity is measured using electrical measuring devices according to DIN 45666.

The specified values refer only to the motor. These values can increase as a result of the overall system vibrational behavior due to installation.



Vibration severity limit values

The speeds of 1800 rpm and 3600 rpm and the associated limit values are specified according to IEC 60034-14. The speeds of 4500 rpm and 6000 rpm and the specified values are defined by the motor manufacturer.

The motors maintain vibration severity grade A up to the rated speed.

##### Balancing according to ISO 21940-32

Apart from the balance quality of the motor, the vibrational quality of motors with attached pulleys is mainly determined by the balance state of the mounted component. If the motor and the mounted component are balanced separately before being joined, the balancing process of the pulley is to be adapted to the motor's balancing type.

SIMOTICS S-1FK2 motors with feather keys are always half-key balanced. In general, motors with a plain shaft are recommended for systems with the most stringent vibrational quality requirements.

##### Vibration stress, imitated vibration values

The requirements of environmental class 3M8 (according to EN 60721-3-3 Table 6) must be maintained for proper function and safeguard the bearing life. The following vibration values must not be exceeded.

- Vibration velocity  $V_{rms}$  according to ISO 10816, max. 4.5 mm/s (0.18 in/s)
- Vibration acceleration  $a_{peak}$  axial and radial 50 m/s<sup>2</sup> (164 ft/s<sup>2</sup>)

During transport, the motors withstand single shocks (6 ms) of up to 250 m/s<sup>2</sup> (820 ft/s<sup>2</sup>).

##### Ambient temperature and installation altitude

Operating range without restrictions:

Temperature range from -15 °C to +40 °C, installation altitude up to 1000 m.

For all other conditions, the permissible torque must be reduced with the aid of the factors given in the table below. The factors refer to the static torque  $M_0$ . The S1 characteristic must be correspondingly shifted in parallel. Intermediate values must be interpolated correspondingly.

Installation altitude above sea level m (ft)	Derating factor at an ambient temperature of			
	30 °C (86 °F)	40 °C (104 °F)	45 °C (113 °F)	50 °C (122 °F)
1000 (3281)	1.05	1	0.97	0.94
2000 (6562)	1	0.95	0.92	0.88

##### Encoder systems

In motors with integrated OCC/DRIVE-CLiQ interface, the sensor signal is already digitally prepared in the motor, and then transferred quickly and without loss to the drive system. Motors with an OCC/DRIVE-CLiQ interface simplify commissioning and diagnostics, as the motor parameters and encoder system are identified automatically.

##### Single-turn absolute encoder

This encoder outputs an absolute angular position between 0° and 360° in the specified resolution. In contrast to the multi-turn absolute encoder, it does not have a revolution counter, and can therefore only supply the position value within one revolution. It does not have a traversing range.

##### Multi-turn absolute encoder

This encoder outputs an absolute angular position between 0° and 360° in the specified resolution. It can also count 4096 revolutions. So with a ball screw, for example, the absolute position of the slide can be determined over a longer distance.

14th position in the Article No. of the motor	Designation	
1FK2 .....-C..	AS20DQC	Absolute encoder 20-bit singleturn (resolution 1048576)
1FK2 .....-D..	AM20DQC	Absolute encoder 20-bit + 12-bit multiturn (resolution 1048576, traversing range 4096 revolutions)

**Technical specifications** (continued)**Holding brake**

Many drives need a holding brake with an EMERGENCY STOP function for safety reasons or to meet process requirements. The brakes used on the SIMOTICS S-1FK2 motors function according to the closed-circuit principle. A spring or permanent magnet exerts a tensile force on the brake armature disk, i.e. in a state of zero current, the brake is closed and the motor shaft thereby stopped.

An electric current that flows through a coil generates an opposing field that counteracts the force effect of the spring or permanent magnet and releases or holds open the brake. Only a limited number of braking operations can be performed for an EMERGENCY STOP or power failure without causing excessive wear on the holding brake. The holding brake is not an opera-

tional brake. Regular dynamic braking leads to increased wear and premature brake failure. In order to ensure the functionality and specification of the brake, neither the total operating energy nor the maximum switching energy per braking operation may be exceeded.

The braking signal is already fully integrated into the SINAMICS S210 converter system, so that an external circuit is not necessary.

After an EMERGENCY STOP sequence with the maximum single switching energy, a cooling time of at least 5 minutes must be allowed.


Motor	Shaft height	Holding torque	Dynamic torque	Opening time	Closing time	Maximum permissible single switching energy	Maximum EMERGENCY STOP speed	Total operating energy (service life)
		Nm (lb <sub>F</sub> -ft)	Nm (lb <sub>F</sub> -ft)	ms	ms	J	rpm	J
1FK2 . 02	20	0.32 (0.24)	0.2 (0.15)	50	15	7.4	8000	500
1FK2 . 03	30	1.3 (0.96)	1.1 (0.81)	90	20	62	7500	5000
1FK2 . 04	40	3.3 (2.43)	3 (2.21)	110	30	268	7500	35000

## SIMOTICS S-1FK2 servomotors


## SIMOTICS S-1FK2 servomotors for SINAMICS S210

## Technical specifications (continued)

## SIMOTICS S-1FK2 shaft height 20



1FK2102-0AG...-A0, 50 W




1FK2102-1AG...-A0, 100 W

## Specific technical specifications

SIMOTICS S-1FK2 servomotors		High Dynamic	
Shaft height 20		1FK2102-0AG...-A0	1FK2102-1AG...-A0
Static torque $M_0$	Nm (lb <sub>F</sub> -ft)	0.16 (0.12)	0.32 (0.24)
Stall current $I_0$	A	0.75	0.76
Maximum torque $M_{max}$	Nm (lb <sub>F</sub> -ft)	0.56 (0.41)	1.11 (0.82)
Maximum current $I_{max}$	A	3.1	3.1
Maximum speed $n_{max}$	rpm	8000	8000
Rotor moment of inertia $J_{Mot}$	kg cm <sup>2</sup> (lb <sub>F</sub> -in <sup>2</sup> )	0.0245 (0.008)	0.036 (0.012)
Moment of inertia (with brake) $J_{Mot Br}$	kg cm <sup>2</sup> (lb <sub>F</sub> -in <sup>2</sup> )	0.0285 (0.010)	0.04 (0.014)
Weight $m_{Mot}$	kg (lb)	0.47 (1.04)	0.60 (1.32)
Weight (with brake) $m_{Mot Br}$	kg (lb)	0.73 (1.61)	0.86 (1.90)
<b>200 ... 240 V 1 AC</b>			
Rated speed $n_{rated}$	rpm	3000	3000
Rated torque $M_{rated}$	Nm (lb <sub>F</sub> -ft)	0.16 (0.12)	0.32 (0.24)
Rated current $I_{rated}$	A	0.75	0.76
Rated power $P_{rated}$	W	50	100
Suitable for SINAMICS S210 servo converter		6SL3210-5HB10-1UF0	6SL3210-5HB10-1UF0



## Dimensional drawings



All dimensions in mm (values in brackets are in inches).

### Technical specifications (continued)

#### Speed/torque characteristics




## SIMOTICS S-1FK2 servomotors


## SIMOTICS S-1FK2 servomotors for SINAMICS S210

## Technical specifications (continued)

## SIMOTICS S-1FK2 shaft height 30



1FK2103-2AG...A0, 200 W




1FK2103-4AG...A0, 400 W

## Specific technical specifications

SIMOTICS S-1FK2 servomotors		High Dynamic		Compact	
Shaft height 30		1FK2103-2AG...A0	1FK2103-4AG...A0	1FK2203-2AG...A0	1FK2203-4AG...A0
Static torque $M_0$	Nm (lb <sub>F</sub> -ft)	0.64 (0.47)	1.27 (0.94)	0.64 (0.47)	1.27 (0.94)
Stall current $I_0$	A	1.36	2.4	1.38	2.52
Maximum torque $M_{max}$	Nm (lb <sub>F</sub> -ft)	1.95 (1.44)	4.05 (2.99)	1.85 (1.36)	3.75 (2.77)
Maximum current $I_{max}$	A	4.8	8.7	4.2	7.8
Maximum speed $n_{max}$	rpm	8000	7300	8000	7800
Rotor moment of inertia $J_{Mot}$	kg cm <sup>2</sup> (lb <sub>F</sub> -in <sup>2</sup> )	0.093 (0.032)	0.139 (0.047)	0.2 (0.068)	0.35 (0.120)
Moment of inertia (with brake) $J_{Mot Br}$	kg cm <sup>2</sup> (lb <sub>F</sub> -in <sup>2</sup> )	0.112 (0.038)	0.158 (0.054)	0.22 (0.075)	0.37 (0.126)
Weight $m_{Mot}$	kg (lb)	1.16 (2.56)	1.63 (3.59)	1.10 (2.43)	1.57 (3.46)
Weight (with brake) $m_{Mot Br}$	kg (lb)	1.66 (3.66)	2.15 (4.74)	1.60 (3.53)	2.10 (4.63)
<b>200 ... 240 V 1 AC</b>					
Rated speed $n_{rated}$	rpm	3000	3000	3000	3000
Rated torque $M_{rated}$	Nm (lb <sub>F</sub> -ft)	0.64 (0.47)	1.27 (0.94)	0.64 (0.47)	1.27 (0.94)
Rated current $I_{rated}$	A	1.36	2.4	1.38	2.52
Rated power $P_{rated}$	W	200	400	200	400
Suitable for SINAMICS S210 servo converter		6SL3210-5HB10-2UF0	6SL3210-5HB10-4UF0	6SL3210-5HB10-2UF0	6SL3210-5HB10-4UF0

## Dimensional drawings







Shaft height 30	DIN IEC	Without brake	With brake	With shaft Ø 14 × 30		With plain shaft Ø 11 × 23 (for IP64 only and without feather key)	
		k LB	k1 LB1	d D	l L	d D	l L
1FK2 . 03-2A... (200 W)		99 (3.9)	130 (5.12)	Ø 14 <sub>h6</sub> (Ø 0.55 <sub>h6</sub> )	30 (1.18)	Ø 11 <sub>k6</sub> (Ø 0.43 <sub>k6</sub> )	23 (0.91)
1FK2 . 03-4A... (400 W)		123 (4.84)	154 (6.06)				

All dimensions in mm (values in brackets are in inches).

### Technical specifications (continued)

#### Speed/torque characteristics




## SIMOTICS S-1FK2 servomotors


## SIMOTICS S-1FK2 servomotors for SINAMICS S210

## Technical specifications (continued)

## SIMOTICS S-1FK2 shaft height 40



1FK2104-4AK...A0, 400 W




1FK2104-5AK...A0, 750 W

## Specific technical specifications

SIMOTICS S-1FK2 servomotors		High Dynamic	
Shaft height 40		1FK2104-4AK...A0	1FK2104-5AK...A0
Static torque $M_0$	Nm (lb <sub>F</sub> -ft)	1.27 (0.94)	2.4 (1.77)
Stall current $I_0$	A	2.4	4.35
Maximum torque $M_{max}$	Nm (lb <sub>F</sub> -ft)	3.85 (2.84)	7.6 (5.61)
Maximum current $I_{max}$	A	8.7	16
Maximum speed $n_{max}$	rpm	7400	7100
Rotor moment of inertia $J_{Mot}$	kg cm <sup>2</sup> (lb <sub>F</sub> -in <sup>2</sup> )	0.35 (0.120)	0.56 (0.191)
Moment of inertia (with brake) $J_{Mot Br}$	kg cm <sup>2</sup> (lb <sub>F</sub> -in <sup>2</sup> )	0.43 (0.147)	0.65 (0.222)
Weight $m_{Mot}$	kg (lb)	2.05 (4.52)	2.85 (6.28)
Weight (with brake) $m_{Mot Br}$	kg (lb)	2.9 (6.39)	3.7 (8.16)
<b>200 ... 240 V 1 AC</b>			
Rated speed $n_{rated}$	rpm	3000	3000
Rated torque $M_{rated}$	Nm (lb <sub>F</sub> -ft)	1.27 (0.94)	2.4 (1.77)
Rated current $I_{rated}$	A	2.4	4.35
Rated power $P_{rated}$	W	400	750
Suitable for SINAMICS S210 servo converter		6SL3210-5HB10-4UF0	6SL3210-5HB10-8UF0

## Dimensional drawings





All dimensions in mm (values in brackets are in inches).



### Technical specifications (continued)

#### Speed/torque characteristics



## SIMOTICS S-1FK2 servomotors

### Notes

3

## MOTION-CONNECT connection systems



### **4/2** MOTION-CONNECT connection systems

- 4/2 Overview
- 4/2 Benefits
- 4/2 Application
- 4/2 Function
- 4/3 Characteristic curves
- 4/4 More information

### **4/5** One Cable Connection (OCC) technology for SINAMICS S210

- 4/5 Overview
- 4/5 Technical specifications
- 4/6 Selection and ordering data

## MOTION-CONNECT connection systems

### MOTION-CONNECT connection systems

#### Overview

MOTION-CONNECT cables are suitable for use with many different types of machine tools and production machinery.

The following variants of MOTION-CONNECT cable are available as fully-assembled power and signal cables or sold by the meter:

- **MOTION-CONNECT 500**
  - Cost-effective solution for predominantly fixed installation
  - Suitable for low mechanical loading
  - Tested for travel distances up to 5 m (16.4 ft)
- **MOTION-CONNECT 800PLUS**
  - Meets requirements for use in cable carriers
  - Suitable for high mechanical loading
  - Oil resistance
  - Tested for travel distances of up to 50 m (164 ft)

#### Benefits

Pre-assembled MOTION-CONNECT cables provide high quality and impeccable system-tested functionality.

#### SPEED-CONNECT

Fast, stable and reliable connections can be made with the new, pre-assembled cables with SPEED-CONNECT connectors. With a short rotation as far as the stop, the cap nut of the connector secures the connection.

The cables with SPEED-CONNECT connectors supplement the established range of MOTION-CONNECT cables with full-thread connectors.

#### Application


MOTION-CONNECT cables are intended for use in machines. They are not suitable for building technology applications or outdoor installation.

MOTION-CONNECT cables have been tested in a cable carrier with horizontal travel distance and have also been designed for this type of application. They are not self-supporting.


The pre-assembled cables can be ordered in length units of 10 cm (3.94 in) and can be extended, if necessary.

When cable lengths (basic cables and extensions) are determined for the systems and applications described in this catalog, the technically permissible maximum cable lengths (e.g. 25 m (82 ft)) specified in the catalog must be observed. Malfunctions can occur if longer cables are used. Siemens assumes no liability for correct transmission of signals or power in this case.

#### Function




The cables must be removed from the drum without twisting, i.e., the cables must be unwound and must never be lifted over the drum flange in loops.



To maximize the service life of the cable carrier and cables, cables in the carrier made from different materials must be separated by spacers in the cable carrier. The spacers must be filled evenly to ensure that the position of the cables does not change during operation. The cables should be distributed as symmetrically as possible according to their weights and dimensions. Cables with very different outer diameters should also be separated by spacers.


When inserting pre-assembled cables into the cable carrier, do not pull at the connector, as this may damage the strain relief or cable clamping.

The cables must not be fixed in the cable carrier. They must be freely movable.



The cables must be able to be moved without applying force in particular in the bending radii of the carrier. The specified minimum bending radius must be adhered to.

## Function (continued)



MOTION-CONNECT cables are tested in a cable carrier. The cables are attached at one end by means of strain relief to the moving ends of the cable carrier. Strain relief is applied over a wide area of the cable jacket surface without crimping the cable.

Cables must be installed in accordance with the instructions supplied by the cable carrier manufacturer.

Note:


If, for example, pre-assembled cables are installed in a cable carrier in such a way that the connector would inhibit assembly, pre-assembled cables without assembled connector can also be supplied (power and signal cables <sup>1)</sup>). Depending on the version, the contacts of the cables are crimped and the connector is supplied separately. After installing the cables, the customer assembles the connector.

In case of vibration load and with horizontal or vertical cable entries, we recommend that the cable is additionally fixed if between the cable strain relief on the cable carrier and the terminal at the motor part of the cable is hanging loose or is not routed. To prevent machine vibrations being transmitted to the connectors, the cable should be fixed at the moving part where the motor is mounted.

## Characteristic curves

**Characteristic curves for MOTION-CONNECT 800PLUS**

The blue area beneath the characteristic curve represents the potential range of use for the cables. The characteristic curves represent the tested operating points.



Permissible acceleration for MOTION-CONNECT 800PLUS signal and power cables up to 16 mm<sup>2</sup>

<sup>1)</sup> Not for DRIVE-CLiQ signal cables.

## MOTION-CONNECT connection systems

### MOTION-CONNECT connection systems

#### More information

##### Current carrying capacity for power and signal cables

The current carrying capacity of PVC/PUR-insulated copper cables is specified for installation types B1, B2, C and E under continuous operating conditions in the table with reference to an

ambient air temperature of 40 °C (104 °F). For other ambient temperatures, the values must be corrected by the derating factors from the table.

Cross-section mm <sup>2</sup>	Current carrying capacity rms AC 50/60 Hz or DC in amps for installation type			
	B1 Single-core cables in conduits or installation ducts	B2 Multi-core cables in conduits or installation ducts	C Multi-core cables, vertically or horizontally on walls/open, without conduits and installation ducts/with contact	E Multi-core cables, horizontally or vertically on perforated cable racks/open, without conduits and installation ducts/with contact
<b>Electronics<sup>1)</sup></b>				
0.2	–	4.3	4.4	4.4
0.5	–	7.5	7.5	7.8
0.75	–	9	9.5	10
<b>Power<sup>2)</sup></b>				
0.75	8.6	8.5	9.8	10.4
1	10.3	10.1	11.7	12.4
1.5	13.5	13.1	15.2	16.1
2.5	18.3	17.4	21	22
4	24	23	28	30
6	31	30	36	37
10	44	40	50	52
16	59	54	66	70


##### Derating factors for power and signal cables

Ambient air temperature °C (°F)	Derating factor according to EN 60204-1, Table D.1
30 (86)	1.15
35 (95)	1.08
40 (104)	1
45 (113)	0.91
50 (122)	0.82
55 (131)	0.71
60 (140)	0.58

<sup>1)</sup> One control circuit pair.

<sup>2)</sup> One symmetrically loaded three-phase AC cable.

## Overview



Motor and converter are simply connected to one another by one cable instead of the usual two or three cables. With this One Cable Technology, energy supply, encoder signals and braking signal are brought together in a single cable. This results in the following advantages:

- Time-saving by laying only one cable
- Smaller installation space and space requirement in cable collars
- Only one cable has to be cleaned. This is advantageous, e.g. in the pharmaceutical industry and where higher requirements are placed upon hygiene
- Can be ordered to the decimeter
- On the motor side, M12 connection plug (smallest OCC connector worldwide) or M17 connection plug
- Rotatable connectors on the motor side
- Motor with very low interfering contour for restricted installation space
- Bending radius optimized to 2.5 × cable diameter static or 4 × cable diameter dynamic for MOTION-CONNECT 800Plus

## Technical specifications



<b>MOTION-CONNECT 500</b>	6FX5002-8QN04-1...	6FX5002-8QN08-1...
<b>Connector</b>		
• Converter side	Siemens IX	Siemens IX
• Motor side	M12 (SPEED-CONNECT)	M17 (SPEED-CONNECT)
<b>Number of cores</b>	10	10
<b>Cable length, max.</b>	50 m (164 ft)	50 m (164 ft)
<b>Cable structure</b>	4G0.38+1Q0.2+1P0.38	4G0.75+1Q0.2+1P0.5
<b>Max. number of bends</b>	100000	100000
<b>Number of disconnection points, max.</b>	3 in 50 m (3 in 164 ft)	3 in 50 m (3 in 164 ft)
<b>Degree of protection</b>		
• Converter side	IP20	IP20
• Motor side	IP65	IP65
<b>Certificates of suitability</b>	RoHS, cURus, CE	RoHS, cURus, CE
<b>Suitable for SIMOTICS S-1FK2 servomotor</b>	Shaft heights 20 and 30	Shaft height 40
<b>MOTION-CONNECT 800PLUS</b>	6FX8002-8QN04-1...	6FX8002-8QN08-1...
<b>Connector</b>		
• Converter side	Siemens IX	Siemens IX
• Motor side	M12 (SPEED-CONNECT)	M17 (SPEED-CONNECT)
<b>Number of cores</b>	10	10
<b>Cable length, max.</b>	50 m (164 ft)	50 m (164 ft)
<b>Cable structure</b>	4G0.38+1Q0.2+1P0.38	4G0.75+1Q0.2+1P0.5
<b>Max. number of bends</b>	10 million	10 million
<b>Number of disconnection points, max.</b>	3 in 50 m (3 in 164 ft)	3 in 50 m (3 in 164 ft)
<b>Degree of protection</b>		
• Converter side	IP20	IP20
• Motor side	IP65	IP65
<b>Certificates of suitability</b>	RoHS, cURus, CE	RoHS, cURus, CE
<b>Suitable for SIMOTICS S-1FK2 servomotor</b>	Shaft heights 20 and 30	Shaft height 40

## MOTION-CONNECT connection systems


### One Cable Connection (OCC) technology for SINAMICS S210

#### Selection and ordering data

##### Motor connection cable

Version	Description	Connector size	$D_{max}$ mm (in)	$r_{static}$ mm (in)	$r_{dynamic}$ mm (in)	For motor	Article No. (Length code see table on page 4/8)
	<b>Pre-assembled OCC motor connection cable MOTION-CONNECT 500 for predominantly fixed routing</b> With SPEED-CONNECT connector (shield connection clamp included in the scope of supply)	M12	9.7 (0.38)	23.5 (0.93)	195 (7.68)	1FK2102 and 1FK2 . 03	<b>6FX5002-8QN04-1</b> ■■■■
		M17	10.5 (0.41)	25.5 (1.00)	195 (7.68)	1FK2104	<b>6FX5002-8QN08-1</b> ■■■■
	<b>Pre-assembled OCC motor connection cable MOTION-CONNECT 800PLUS for use with cable carriers</b> With SPEED-CONNECT connector (shield connection clamp included in the scope of supply)	M12	9.7 (0.38)	28.2 (1.11)	37.6 (1.48)	1FK2102 and 1FK2 . 03	<b>6FX8002-8QN04-1</b> ■■■■
		M17	10.5 (0.41)	30.6 (1.20)	40.8 (1.61)	1FK2104	<b>6FX8002-8QN08-1</b> ■■■■
	<b>OCC motor connection cable MOTION-CONNECT 500 for predominantly fixed routing</b> With SPEED-CONNECT connector and with connector supplied on the converter side (shield connection clamp included in the scope of supply) <sup>1)</sup>	M12	9.7 (0.38)	23.5 (0.93)	195 (7.68)	1FK2102 and 1FK2 . 03	<b>6FX5012-8QN04-1</b> ■■■■
		M17	10.5 (0.41)	25.5 (1.00)	195 (7.68)	1FK2104	<b>6FX5012-8QN08-1</b> ■■■■
	<b>OCC motor connection cable MOTION-CONNECT 800PLUS for use with cable carriers</b> With SPEED-CONNECT connector and with connector supplied on the converter side (shield connection clamp included in the scope of supply) <sup>1)</sup>	M12	9.7 (0.38)	28.2 (1.11)	37.6 (1.48)	1FK2102 and 1FK2 . 03	<b>6FX8012-8QN04-1</b> ■■■■
		M17	10.5 (0.41)	30.6 (1.20)	40.8 (1.61)	1FK2104	<b>6FX8012-8QN08-1</b> ■■■■

##### Extension cable

Version	Description	Connector size	$D_{max}$ mm (in)	$r_{static}$ mm (in)	$r_{dynamic}$ mm (in)	For motor	Article No. (Length code see table on page 4/8)
	<b>Pre-assembled OCC extension cable MOTION-CONNECT 500 for predominantly fixed routing</b> with SPEED-CONNECT connectors	M12	9.7 (0.38)	23.5 (0.93)	195 (7.68)	1FK2102 and 1FK2 . 03	<b>6FX5002-8QE04-1</b> ■■■■
		M17	10.5 (0.41)	25.5 (1.00)	195 (7.68)	1FK2104	<b>6FX5002-8QE08-1</b> ■■■■
	<b>Pre-assembled OCC extension cable MOTION-CONNECT 800PLUS for use with cable carriers</b> with SPEED-CONNECT connectors	M12	9.7 (0.38)	28.2 (1.11)	37.6 (1.48)	1FK2102 and 1FK2 . 03	<b>6FX8002-8QE04-1</b> ■■■■
		M17	10.5 (0.41)	30.6 (1.20)	40.8 (1.61)	1FK2104	<b>6FX8002-8QE08-1</b> ■■■■







<sup>1)</sup> Available soon.



## Selection and ordering data (continued)

## Accessories

## OCC components for customer assembly

Version	Description	For motor	Article No. (Length code see table on page 4/8)
	<b>Sold by the meter OCC line MOTION-CONNECT 500</b>	1FK2102 and 1FK2 . 03	<b>6FX5008-1BE04-1</b> ■■■■
	For the self-assembly of motor connection or extension cables MOTION-CONNECT 500 predominantly for fixed routing (see table for length codes) <sup>1)</sup>	1FK2104	<b>6FX5008-1BE08-1</b> ■■■■
	<b>Sold by the meter OCC line MOTION-CONNECT 800PLUS</b>	1FK2102 and 1FK2 . 03	<b>6FX8008-1BE04-1</b> ■■■■
	For the self-assembly of motor connection or extension cables MOTION-CONNECT 800PLUS for use with cable carriers (see table for length codes) <sup>1)</sup>	1FK2104	<b>6FX8008-1BE08-1</b> ■■■■
	<b>Motor-side M12 SPEED-CONNECT connector</b> 10-pole, including all socket contacts <sup>1)</sup>	1FK2102 and 1FK2 . 03	<b>6FX2003-0LU64</b>
	<b>Motor-side M17 SPEED-CONNECT connector</b> 10-pole, including all socket contacts <sup>1)</sup>	1FK2104	<b>6FX2003-0LU54</b>
	<b>M12 SPEED-CONNECT connector with external thread for extension cable</b> 10-pole, including all pin contacts <sup>1)</sup>	1FK2102 and 1FK2 . 03	<b>6FX2003-0LA64</b>
	<b>M17 SPEED-CONNECT connector with external thread for extension cable</b> 10-pole, including all pin contacts <sup>1)</sup>	1FK2104	<b>6FX2003-0LA54</b>
	<b>Converter-side Siemens IX signal connector</b> Device version in insulation displacement technology for field assembly <sup>1)</sup>	–	<b>6FX2003-0DE01</b>
	<b>Shield clamp</b> For attaching the connection cables to the shield plate of the converter (packing unit 10 items)	–	<b>6FX2003-7EX10</b>


<sup>1)</sup> Available soon.

## MOTION-CONNECT connection systems

### One Cable Connection (OCC) technology for SINAMICS S210

#### Selection and ordering data (continued)

##### Control cabinet bushing

Version	Description	For motor	Article No.
	<b>Mounting flange</b> For control cabinet bushing for M12 connector size	1FK2102 and 1FK2 . 03	<b>6FX2003-7JX00</b>
	<b>Mounting flange</b> For control cabinet bushing for M17 connector size	1FK2104	<b>6FX2003-7HX00</b>

##### Length code (max. 50 m (164 ft))

Description	Article No. supplement
<b>MOTION-CONNECT cable</b>	<b>6FX . 0 . 2-8Q . 0 . -1 ■ ■ ■</b>
0 m (0 ft)	<b>A</b>
10 m (32.8 ft)	<b>B</b>
20 m (65.6 ft)	<b>C</b>
30 m (98.4 ft)	<b>D</b>
40 m (131 ft)	<b>E</b>
50 m (164 ft)	<b>F</b>
0 m (0 ft)	<b>A</b>
1 m (3.28 ft)	<b>B</b>
2 m (6.56 ft)	<b>C</b>
3 m (9.84 ft)	<b>D</b>
4 m (13.1 ft)	<b>E</b>
5 m (16.4 ft)	<b>F</b>
6 m (19.7 ft)	<b>G</b>
7 m (23.0 ft)	<b>H</b>
8 m (26.2 ft)	<b>J</b>
9 m (29.5 ft)	<b>K</b>
0 m (0 ft)	<b>0</b>
0.1 m (0.33 ft)	<b>1</b>
0.2 m (0.66 ft)	<b>2</b>
0.3 m (0.98 ft)	<b>3</b>
0.4 m (1.31 ft)	<b>4</b>
0.5 m (1.64 ft)	<b>5</b>
0.6 m (1.97 ft)	<b>6</b>
0.7 m (2.30 ft)	<b>7</b>
0.8 m (2.62 ft)	<b>8</b>

## Engineering tools



### Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, systems, machines and networks.

In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial security concept. Siemens' products and solutions constitute one element of such a concept.

Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place.

For additional information on industrial security measures that may be implemented, please visit

<https://www.siemens.com/industrialsecurity>

Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats.

To stay informed about product updates, subscribe to the Siemens Industrial Security RSS Feed under

<https://www.siemens.com/industrialsecurity>

5/2

**Drive Technology Configurator**

5/3

**SINAMICS Web server  
for SINAMICS S210**


## Engineering tools

### Drive Technology Configurator

#### Overview

The Drive Technology Configurator (DT Configurator) helps you to configure the optimum drive technology products for your application – starting with gear units, motors, inverters as well as the associated options and components and ending with controllers, software licenses and connection systems. Whether with little or detailed knowledge of products: preselected product groups, deliberate navigation through selection menus and direct product selection through entry of the article number support quick, efficient and convenient configuration.

In addition, comprehensive documentation comprising technical data sheets, 2D dimensional drawings/3D CAD models, operating instructions, certificates, etc. can be selected in the DT Configurator. Immediate ordering is possible by simply transferring a parts list to the shopping cart of the Industry Mall.



#### Drive Technology Configurator for efficient drive configuration with the following functions

- Quick and easy configuration of drive products and associated components – gear units, motors, inverters, controllers, connection systems
- Configuration of drive systems for pumps, fans and compressor applications from 1 kW to 2.6 MW
- Retrievable documentation for configured products and components, such as
  - Data sheets in up to 9 languages in PDF or RTF format
  - 2D dimensional drawings/3D CAD models in various formats
  - Terminal box drawing and terminal connection diagram
  - Operating instructions
  - Certificates
  - Start-up calculation for SIMOTICS motors
  - EPLAN macros
- Support with retrofitting in conjunction with Spares On Web ([www.siemens.com/sow](http://www.siemens.com/sow))
- Ability to order products directly through the Siemens Industry Mall

#### Access to the Drive Technology Configurator

The Drive Technology Configurator can be called up without registration and without a login:

[www.siemens.com/dt-configurator](http://www.siemens.com/dt-configurator)

#### Selection and ordering data

Description	Article No.
<b>Interactive Catalog CA 01</b> on DVD-ROM including Drive Technology Configurator English	<b>E86060-D4001-A510-D8-7600</b>

#### More information

[Online access to the Drive Technology Configurator](#)

More information about the Drive Technology Configurator is available on the Internet at

[www.siemens.com/dtconfigurator](http://www.siemens.com/dtconfigurator)

[Offline access to the Drive Technology Configurator in the Interactive Catalog CA 01](#)

In addition, the Drive Technology Configurator is also included in the Interactive Catalog CA 01 on DVD-ROM – the offline version of the Siemens Industry Mall.

The Interactive Catalog CA 01 can be ordered from the relevant Siemens sales office or via the Internet:


[www.siemens.com/automation/CA01](http://www.siemens.com/automation/CA01)

## Overview

### *Web server for efficient commissioning, diagnostics and maintenance – available anywhere, anytime*

Thanks to the web server, the SINAMICS S210 drive system offers efficient commissioning, diagnostics and maintenance options. The web server provides access to a multi-faceted range of new options for parameter assignment, drive diagnostics and remote maintenance for any networked PC with a web browser or for tablets and smartphones (via a separate WLAN access point), including:

- Simple and fast commissioning
- Drive traversing via the control panel
- Downloading/uploading a configuration
- Providing a status overview of the drive
- Evaluating warnings and fault messages
- Monitoring and adapting parameter settings



Integration of the SINAMICS web server as shown by the example of SINAMICS S120, SINAMICS S210 and PROFINET communication

The SINAMICS web server is available as of SINAMICS S210 firmware V5.1.

## Benefits

### Simple and fast commissioning

- No installation of additional commissioning software
- Simple controller optimization with One Button Tuning
- Standard pages for limit values and settings
- Comprehensive fault diagnosis

### Shorter machine downtimes

- Efficient diagnostics and maintenance

### Direct language selection

- English, German, Italian (Chinese, French and Spanish available soon)

### Accessibility

- Via all LAN or PROFINET interfaces
- Tablet and smartphone access via WLAN with separate access point

### Two users with different rights profiles

- e. g. for operators and service personnel

### Diagnostic functions

- Quick overview of the current configuration and the state of the drive
- Understandable diagnostic information and messages, including the causes of issues and possible remedies, are displayed in plain text in multiple languages

### Freely configurable parameter lists

- Monitoring parameters for diagnostic purposes, for example for operating personnel
- Adjustment of the parameter lists using filters, parameter groups and the configuration of personal lists

### Access security

- Protection against unauthorized access to the drive information


## Application

The web server is ideal for applications in which special commissioning software or version dependencies are not desired. Easy commissioning, diagnostics and maintenance are possible both locally and remotely, provided appropriate security measures are applied.

## Engineering tools

### Notes


## Services and documentation



<b>6/2</b>	<b>Partner at Siemens</b>
<b>6/3</b>	<b>Online Services</b>
6/3	Information and ordering options on the Internet and DVD
6/4	Information and Download Center, Social Media, Mobile Media
<b>6/5</b>	<b>Industry Services</b>
6/6	Industry Services – Portfolio overview
6/8	Online Support
<b>6/9</b>	<b>Training</b>
6/9	SITRAIN – Training for Industry
6/10	SINAMICS S210 training case
<b>6/11</b>	<b>Applications</b>
<b>6/12</b>	<b>Partners for Drives Options</b>
<b>6/13</b>	<b>mySupport documentation</b>
<b>6/14</b>	<b>Documentation</b>
6/15	General documentation
6/15	SINAMICS S210 documentation

## Services and documentation

### Partner at Siemens



At Siemens we are resolutely pursuing the same goal: long-term improvement of your competitive ability. We are committed to this goal. Thanks to our commitment, we continue to set new standards in automation and drive technology. In all industries – worldwide.

At your service locally, around the globe for consulting, sales, training, service, support, spare parts on the entire portfolio of Digital Factory and Process Industries and Drives.



Your partner can be found in our Personal Contacts Database at: [www.siemens.com/automation-contact](http://www.siemens.com/automation-contact)

You start by selecting

- the required competence,
- products and branches,
- a country,
- a city


or by a

- location search or
- person search.





#### The Future of Manufacturing on the Internet




Detailed knowledge of the range of products and services available is essential when planning and engineering automation systems. It goes without saying that this information must always be as up-to-date as possible.

Industry is on the threshold of the fourth industrial revolution as digitization now follows after the automation of production. The goals are to increase productivity and efficiency, speed, and quality. In this way, companies can remain competitive on the path to the future of industry.

You will find everything you need to know about products, systems and services on the internet at:

[www.siemens.com/industry](http://www.siemens.com/industry)

#### Product Selection Using the Interactive CA 01 Automation and Drives Catalog



Detailed information together with user-friendly interactive functions:

The CA 01 interactive catalog covers more than 100,000 products, thus providing a comprehensive overview of the product range provided by Siemens.

You will find everything you need here for solving tasks in the fields of automation, switching, installation and drives. All information is provided over a user interface that is both user-friendly and intuitive.

You can order the CA 01 product catalog from your Siemens sales contact or in the Information and Download Center:


[www.siemens.com/industry/infocenter](http://www.siemens.com/industry/infocenter)

Information about the CA 01 interactive catalog can be found on the Internet at:

[www.siemens.com/automation/ca01](http://www.siemens.com/automation/ca01)

or on DVD.

#### Easy Shopping with the Industry Mall



The Industry Mall is the electronic ordering platform of Siemens AG on the Internet. Here you have online access to a huge range of products presented in an informative and attractive way.

Data transfer via EDIFACT allows the whole procedure, from selection through ordering to tracking and tracing, to be carried out online. Availability checks, customer-specific discounts and bid creation are also possible.

Numerous additional functions are provided for your support. For example, powerful search functions make it easy to select the required products. Configurators enable you to configure complex product and system components quickly and easily. CAx data types are also provided here.

You can find the Industry Mall on the Internet at:


[www.siemens.com/industrymall](http://www.siemens.com/industrymall)

## Services and documentation

### Online Services

#### Information and Download Center, Social Media, Mobile Media

##### Downloading Catalogs




In addition to numerous other useful documents, you can also find the catalogs listed on the back inside cover of this catalog in the Information and Download Center. You can download these catalogs in PDF format without having to register.

The filter dialog above the first catalog displayed makes it possible to carry out targeted searches. If you enter "MD 3" for example, you will find both the MD 30.1 and MD 31.1 catalogs. If you enter "IC 10", both the IC 10 catalog and the associated news or add-ons are displayed.

Visit us at:

[www.siemens.com/industry/infocenter](http://www.siemens.com/industry/infocenter)

##### Social and Mobile Media



Connect with Siemens through social media: visit our social networking sites for a wealth of useful information, demos on products and services, the opportunity to provide feedback, to exchange information and ideas with customers and other Siemens employees, and much, much more. Stay in the know and follow us on the ever-expanding global network of social media.

To find out more about Siemens' current social media activities, visit us at:

[www.siemens.com/socialmedia](http://www.siemens.com/socialmedia)

Or via our product pages at:

[www.siemens.com/automation](http://www.siemens.com/automation) or [www.siemens.com/drives](http://www.siemens.com/drives)

Here you can read all the news on the future of the industry, watch current videos and obtain information about all the latest industry developments.

[www.siemens.com/future-of-manufacturing](http://www.siemens.com/future-of-manufacturing)


Discover the world of Siemens.


We are also constantly expanding our offering of cross-platform apps for smartphones and tablets. You will find the current Siemens apps at the App Store (iOS) or at Google Play (Android):

<https://itunes.apple.com/en/app/siemens/id452698392?mt=8>

<https://play.google.com/store/search?q=siemens>

The Siemens app, for example, tells you all about the history, latest developments and future plans of the company – with informative pictures, fascinating reports and the most recent press releases.



**Overview**

**Keep your business running and shaping your digital future – with Industry Services**

Optimizing the productivity of your equipment and operations can be a challenge, especially with constantly changing market conditions. Working with our service experts makes it easier. We understand your industry's unique processes and provide the services needed so that you can better achieve your business goals.

You can count on us to maximize your uptime and minimize your downtime, increasing your operations' productivity and reliability. When your operations have to be changed quickly to meet a new demand or business opportunity, our services give you the flexibility to adapt. Of course, we take care that your production is protected against cyber threats. We assist in keeping your operations as energy and resource efficient as possible and reducing your total cost of ownership. As a trendsetter, we ensure that you can capitalize on the opportunities of digitalization and by applying data analytics to enhance decision making: You can be sure that your plant reaches its full potential and retains this over the longer lifespan.

You can rely on our highly dedicated team of engineers, technicians and specialists to deliver the services you need – safely, professionally and in compliance with all regulations. We are there for you, where you need us, when you need us.

<https://www.siemens.com/global/en/home/products/services/industry.html>


## Services and documentation

### Industry Services

#### Industry Services – Portfolio overview

##### Overview

#### Digital Services



Digital Services make your industrial processes transparent to gain improvements in productivity, asset availability, and energy efficiency.

Production data is generated, filtered and translated with intelligent analytics to enhance decision-making.

This is done whilst taking data security into consideration and with continuous protection against cyber-attack threats.

<https://www.siemens.com/global/en/home/products/services/industry/digital-services.html>

#### Training Services



From the basics and advanced to specialist skills, SITRAIN courses provide expertise right from the manufacturer – and encompass the entire spectrum of Siemens products and systems for the industry.

Worldwide, SITRAIN courses are available wherever you need a training course in more than 170 locations in over 60 countries.

<https://support.industry.siemens.com/cs/ww/en/sc/2226>

#### Support and Consulting Services



**Industry Online Support** site for comprehensive information, application examples, FAQs and support requests.

**Technical and Engineering Support** for advice and answers for all inquiries about functionality, handling, and fault clearance. The Service Card as prepaid support for value added services such as Priority Call Back or Extended Support offers the clear advantage of quick and easy purchasing.

**Information & Consulting Services**, e.g. SIMATIC System Audit; clarity about the state and service capability of your automation system or Lifecycle Information Services; transparency on the lifecycle of the products in your plants.

<https://support.industry.siemens.com/cs/ww/en/sc/2235>

#### Spare Parts Services



Spare Parts Services are available worldwide for smooth and fast supply of spare parts – and thus optimal plant availability. Genuine spare parts are available for up to ten years. Logistic experts take care of procurement, transport, custom clearance, storage and order management. Reliable logistics processes ensure that components reach their destination as needed.

Since not all spare parts can be kept in stock at all times, Siemens offers a preventive measure for spare parts provisioning on the customer's premises with optimized **Spare Parts Packages** for individual products, custom-assembled drive components and entire integrated drive trains – including risk consulting.

**Asset Optimization Services** help you design a strategy for parts supply where your investment and carrying costs are reduced and the risk of obsolescence is avoided.

<https://support.industry.siemens.com/cs/ww/en/sc/2110>

#### Overview (continued)

##### Repair Services



Repair Services are offered on-site and in regional repair centers for fast restoration of faulty devices' functionality.

Also available are extended repair services, which include additional diagnostic and repair measures, as well as emergency services.

<https://support.industry.siemens.com/cs/ww/en/sc/2154>

##### Retrofit and Modernization Services




Provide a cost-effective solution for the expansion of entire plants, optimization of systems or upgrading existing products to the latest technology and software, e.g. migration services for automation systems.

Service experts support projects from planning through commissioning and, if desired over the entire extended lifespan, e.g. Retrofit for Integrated Drive Systems for an extended lifetime of your machines and plants.

<https://support.industry.siemens.com/cs/ww/de/sc/2286>

##### Field and Maintenance Services



Siemens specialists are available globally to provide expert field and maintenance services, including commissioning, functional testing, preventive maintenance and fault clearance.

All services can be included in customized service agreements with defined reaction times or fixed maintenance intervals.

<https://support.industry.siemens.com/cs/ww/en/sc/2265>

##### Service Programs and Agreements



A technical Service Program or Agreement enables you to easily bundle a wide range of services into a single annual or multi-year agreement.

You pick the services you need to match your unique requirements or fill gaps in your organization's maintenance capabilities.

Programs and agreements can be customized as KPI-based and/or performance-based contracts.

<https://support.industry.siemens.com/cs/ww/de/sc/2275>

## Services and documentation

Industry Services

### Online Support

#### Overview

Online Support – fast, intuitive, whenever you want, wherever you need

**Web**

[support.industry.siemens.com](http://support.industry.siemens.com)

**App**

Scan the QR code for information on our Online Support app.

- FAQ / Application examples**  
Information about industrial products, programming and configuration as well as application examples
- Technical Information**  
Videos, documentation, manuals, updates, product notes, compatibility tool, certificates, planning data such as dimensional drawings, product data, 3D models
- Forum**  
Exchange information and experience with other users and experts

## Online Support for Siemens Products for Industry

Siemens Industry and Online Support with some 1.7 million visitors per month is one of the most popular web services provided by Siemens. It is the central access point for comprehensive technical know-how about products, systems and services for automation and drives applications as well as for process industries.

In connection with the challenges and opportunities related to digitalization you can look forward to continued support with innovative offerings.

6

**Overview**

***Your benefit from practical training directly from the manufacturer***

SITRAIN – Training for Industry – provides you with comprehensive support in solving your tasks.

Training directly from the manufacturer enables you to make correct decisions with confidence.

***Increased profits and lower costs:***

- Shorter times for commissioning, maintenance and servicing
- Optimized production operations
- Reliable configuration and commissioning
- Shortened startup times, reduced downtimes, and faster troubleshooting
- Exclude expensive faulty planning right from the start
- Flexible plant adaptation to market requirements
- Compliance with quality standards in production
- Increased employee satisfaction and motivation
- Shorter familiarization times following changes in technology and staff

***Contact***

Visit our site on the Internet at:  
[www.siemens.com/sitrain](http://www.siemens.com/sitrain)

or let us advise you personally. You can request our latest training catalog from:

***SITRAIN – Training for Industry***  
***SITRAIN Customer Support Germany:***

Tel.: +49 911 895-7575

Fax: +49 911 895-7576

Email: [info@sitrain.com](mailto:info@sitrain.com)

***Your benefits with SITRAIN – Training for Industry***
Certified top trainers

Our trainers are skilled specialists with practical experience. Course developers have close contact with product development, and pass on their knowledge to the trainers and then to you.

Practical application with practice

Practice, practice, practice! We have designed the trainings with an emphasis on practical exercises. They take up to half of the course time in our trainings. You can therefore implement your new knowledge in practice even faster.

300 courses in more than 60 countries

We offer a total of about 300 classroom-based courses. You can find us at more than 50 locations in Germany, and in 62 countries worldwide. You can find which course is offered at which location at:

[www.siemens.com/sitrain](http://www.siemens.com/sitrain)

Skills development

Do you want to develop skills and fill in gaps in your knowledge? Our solution: We will provide a program tailored exactly to your personal requirements. After an individual requirements analysis, we will train you in our training centers near you or directly at your offices. You will practice on the most modern training equipment with special exercise units. The individual training courses are optimally matched to each other and help with the continuous development of knowledge and skills. After finishing a training module, the follow-up measures make success certain, as well as the refreshment and deepening of the knowledge gained.

## Services and documentation

### Training

#### SINAMICS S210 training case

##### Overview



The SINAMICS S210 training case is a convincing demonstration system thanks to its compact design. It is suitable for direct presentations as well as for tests in technical departments. The training case enables the functions of SINAMICS S210 servo drive system to be demonstrated and tested quickly and easily.

It contains the following components:

- 2 × SINAMICS S210 servo converters, 0.1 kW, 230 V 1 AC
- 2 × SIMOTICS S-1FK2 servomotors, High Dynamic
- 2 × One Cable Connection (OCC) motor connection cable
- Rail, prepared for installation of a controller, e.g. SIMATIC S7-1500 (controller not included in scope of supply)

The SINAMICS S210 training case is supplied as a trolley with a hood.

##### Technical specifications

SINAMICS S210 training case	Article No. available soon The training case can currently only be ordered internally via SIDEMO under the material number A5E42367671. <a href="http://www.siemens.com/sidemo">www.siemens.com/sidemo</a>
<b>Supply voltage</b>	230 V 1 AC
<b>Dimensions</b>	
• Width	42 cm (16.54 in)
• Height	58 cm (22.83 in)
• Depth	34 cm (13.39 in)
<b>Weight, approx.</b>	21 kg (46.3 lb)

##### Selection and ordering data

Description	Article No.
<b>SINAMICS S210 training case</b>	Available soon The training case can currently only be ordered internally via SIDEMO under the material number A5E42367671. <a href="http://www.siemens.com/sidemo">www.siemens.com/sidemo</a>



### Overview



Our understanding of an application is the customer-specific solution of an automation task based on standard hardware and software components. In this respect, industry knowledge and technological expertise are just as important as expert knowledge about how our products and systems work. We are setting ourselves this challenge with more than 280 application engineers in 20 countries.

#### Application centers

We currently have application centers in:

- Germany: Head Office in Erlangen and in other German regions, e.g. in Munich, Nuremberg, Stuttgart, Mannheim, Frankfurt, Chemnitz, Cologne, Bielefeld, Bremen, Hanover, Hamburg
- Belgium: Brussels
- Brazil: Sao Paulo
- China: Beijing and 12 regions
- Denmark: Ballerup
- France: Paris
- Great Britain: Manchester
- India: Mumbai
- Italy: Bologna, Milan
- Japan: Tokyo, Osaka
- The Netherlands: The Hague
- Austria: Vienna
- Poland: Warsaw
- Sweden: Göteborg
- Switzerland: Zurich, Lausanne
- Spain: Madrid
- South Korea: Seoul
- Taiwan: Taipei
- Turkey: Istanbul
- USA: Atlanta

These application centers specialize in the use of SIMATIC/SIMOTION/SINAMICS. You therefore can rely on automation and drive specialists for implementing successful applications. By involving your personnel at an early stage in the process, we can provide a solid basis for rapid knowledge transfer, maintenance and further development of your automation solution.

#### Advice on applications and implementation

We offer a variety of consultation services to help you find the optimum solution for the SIMATIC/SIMOTION/SINAMICS application you want to implement:

The quotation phase includes

- clarification of technical questions,
- discussion of machine concepts and customer-specific solutions,
- selection of suitable technology and
- suggestions for implementation.

A technical feasibility study is also performed at the outset. In this way, difficult points of the application can be identified and solved early on. We can also configure and implement your application as a complete solution from a single source.

A large number of proven standard applications are available for use during the implementation phase. This saves engineering costs.

The system can be commissioned by experienced, competent personnel, if required. This saves time and trouble.

If servicing is required, we can support you on site or remotely. For further information about servicing, please see the section "Industry Services".

#### On-site application training

Training for the implemented applications can also be organized and carried out on site. This training for machine manufacturers and their customers does not deal with individual products, but the entire hardware and software system (for example, automation, drives and visualization).

From an initial concept to successful installation and commissioning: We provide complete support for SIMATIC/SIMOTION/SINAMICS! Contact your Siemens representative.

You can find further information at [www.siemens.com/machinebuilding](http://www.siemens.com/machinebuilding)

## Services and documentation

### Partners for Drives Options

#### Overview

##### *Siemens Product Partners for Drives Options*

###### Individual options for our drives


In order to meet as many customer requirements as possible in the field of drive technology, in addition to its own products, Siemens also relies on the individual and complementary services of selected partners.

We are increasingly focusing on the standard drive options, and our Siemens Product Partners for Drives Options supplement our drives with individual drive options.

This gives Siemens a unique flexibility to meet all application requirements. Naturally, we support our Siemens Product Partners for Drives Options in tailoring their options perfectly to our drives.

For you as our customer, there are multiple benefits:

- The Siemens Product Partners for Drives Options meet the same high standards of quality and performance that we place on our own products
- Drive options can be adapted to individual requirements/designs
- The Siemens Product Partners for Drives Options know our Siemens inverter portfolio and can advise you individually and quickly




## 6

#### More information

You can find more information on the Internet at [www.siemens.com/drives-options-partner](http://www.siemens.com/drives-options-partner)

### Overview

#### mySupport documentation – Compiling personal documents



mySupport documentation is a web-based system for generating personalized documentation based on standard documents and is part of the Siemens Industry Online Support portal.

In mySupport, a personal document library can be created in the "Documentation" category. This library can be accessed online in mySupport or also be generated in various formats for offline use.

Previously, this functionality was available in the My Documentation Manager for configurable manuals. Due to the integration in mySupport, all entries of the Industry Online Support can now be imported into the personal document library, including FAQs or product notifications.

If you have already worked with the My Documentation Manager, all of the previously created libraries will continue to be available without restrictions in mySupport.

In addition, the personal library in mySupport can be shared with other mySupport users. In this way, a collection of relevant documents can be created very effectively and used together with other mySupport users all over the world.

You must register/log in for configuring and generating/managing.

### Benefits

- Display  
View, print or download standard documents or personalized documents
- Configure  
Transfer standard documents or parts of them to personalized documents
- Generate/Manage  
Generate and manage personalized documents in the formats PDF, RTF or XML in all available languages

### Function

#### Opening mySupport documentation in the Industry Online Support portal

- About the product support, entry type "Manual":  
<https://support.industry.siemens.com/cs/ww/en/ps/manual>  
By clicking on the required version of the manual and then "Show and configure", the manual opens in a modular view, where you can navigate from topic to topic. Here the direct link to a topic can be used and made available to other users. The selected document can be added to the personal library via "mySupport Cockpit" > "Add to mySupport documentation".
- Via the direct link  
<https://support.industry.siemens.com/my/ww/en/documentation/advanced>  
After logon/registration, the online help is displayed as the current document.

### More information

You can find additional information on the Internet at

- <https://support.industry.siemens.com/my/ww/en/documentation>
- [https://support.industry.siemens.com/cs/helpcenter/en/index.htm?#persoenliche\\_bibliothek\\_aufbauen.htm](https://support.industry.siemens.com/cs/helpcenter/en/index.htm?#persoenliche_bibliothek_aufbauen.htm)

## Services and documentation

### Documentation

#### Overview

A high-quality programmable control or drive system can be used to maximum effect only if the user is aware of the performance of the products used as a result of intensive training and good technical documentation.

This is becoming more important due to the shorter innovation cycles of modern automation products and the convergence of electronics and mechanical engineering.

A comprehensive range of documentation is available which includes a Getting Started guide, operating instructions, installation manuals and a list manual.

The documents are available in hardcopy form or as a PDF file for downloading from the Internet.

Information and documentation relating to SINUMERIK, SINAMICS, SIMOTION and SIMOTICS are available on the Internet at <https://support.industry.siemens.com/cs/document/109476679>

In addition to many other useful documents, the Information and Download Center also contains catalogs about the following systems:

- SINUMERIK: NC 62, NC 81.1, NC 82
- SINAMICS: D 11, D 12, D 21.3, D 21.4, D 23.1, D 23.2, D 31.1, D 31.2, D 32, D 35
- SIMOTION: PM 21
- SIMOTICS: D 21.4, D 41, D 81.1, D 81.8, D 83.1

You can download these catalogs in PDF format – you don't need to log on. You can perform a targeted search using the filter box above the first displayed catalog. By entering the search term "NC 8", for example, you can locate Catalog NC 81.1 and Catalog NC 82, and by entering "ST 70" you will find Catalog ST 70 as well as the relevant news and add-ons (if available). [www.siemens.com/industry/infocenter](http://www.siemens.com/industry/infocenter)

#### Application

##### *Explanations of the manuals:*

- **Operating Instructions**  
contain all the information needed to install the device and make electrical connections, information about commissioning and a description of the inverter functions.  
Phases of use: Control cabinet construction, commissioning, operation, maintenance and servicing.
- **Hardware Installation Manual**  
contains all relevant information about the intended use of the components of a system (technical specifications, interfaces, dimensional drawings, characteristics, or possible applications), information about installation and electrical connections and information about maintenance and servicing.  
Phases of use: Control cabinet configuration/construction, maintenance and servicing.
- **Operating and Installation Instructions** (for inverter and accessories)  
contain all relevant information about the intended use of the components, such as technical specifications, interfaces, dimensional drawings, characteristics, or possible applications.  
Phases of use: Control cabinet configuration/construction.
- **Manual/Configuration Manual**  
contains all necessary information about the intended use of the components of a system, e.g. technical specifications, interfaces, dimensional drawings, characteristics, or possible applications.  
Phases of use: Cabinet configuration/setup, circuit diagram configuration/drawing.
- **Commissioning Manual**  
contains all information relevant to commissioning after installation and wiring. It also contains all safety and warning notices relevant to commissioning in addition to overview drawings.  
Phases of use: Commissioning of components that have already been connected, configuration of system functions.
- **List Manual**  
contains all parameters, function diagrams, and faults/alarms for the product/system as well as their meanings and setting options. It contains parameter data and fault/alarm descriptions with functional correlations.  
Phases of use: Commissioning of components that have already been connected, configuration of system functions, fault cause/diagnosis.
- **Getting Started**  
provides information about getting started for the first-time user as well as references to additional information. It contains information about the basic steps to be taken during commissioning. The information in the other documentation should be carefully observed for all of the other work required.  
Phases of use: Commissioning of components that have already been connected.
- **Function Manual Drive Functions**  
contains all the relevant information about individual drive functions: Description, commissioning and integration in the drive system.  
Phases of use: Commissioning of components that have already been connected, configuration of system functions.

**Overview**

Description	Article No.
<b>Automating with PROFINET: Industrial Communication Based on Industrial Ethernet</b> <ul style="list-style-type: none"> <li>• German</li> <li>• English</li> </ul>	Via bookstore  <b>ISBN 978-3-89578-293-0</b> <b>ISBN 978-3-89578-294-7</b>
<b>Configuration Manual EMC Installation Guideline SIMOCRANE, SIMOTICS, SIMOTION, SINAMICS, SINUMERIK</b> <ul style="list-style-type: none"> <li>• German</li> <li>• English</li> <li>• Italian</li> <li>• French</li> <li>• Spanish</li> <li>• Chinese Simplified</li> </ul>	<b>6FC5297-0AD30-0AP3</b> <b>6FC5297-0AD30-0BP3</b> <b>6FC5297-0AD30-0CP3</b> <b>6FC5297-0AD30-0DP3</b> <b>6FC5297-0AD30-0EP3</b> <b>6FC5297-0AD30-0RP3</b>

**SINAMICS S210 documentation**
**Overview**

A **Quick Installation Guide** is supplied in hard copy form in English with every SINAMICS S210. Further documentation, such as the operating instructions, is available free on the Internet at:

[www.siemens.com/sinamics-s210/documentation](http://www.siemens.com/sinamics-s210/documentation)

Detailed information on the SINAMICS S210 servo drive system, including the latest technical documentation (brochures, dimensional drawings, certificates, manuals and operating instructions), is available on the Internet at:

[www.siemens.com/sinamics-s210](http://www.siemens.com/sinamics-s210)

and is also available via the Drive Technology Configurator (DT Configurator).

The DT Configurator can be found in the Siemens Industry Mall at the following address:

[www.siemens.com/dt-configurator](http://www.siemens.com/dt-configurator)

## Services and documentation

### Notes

## Appendix



7/2	<b>Certificates of suitability (approvals)</b>
7/4	<b>Software licenses</b>
7/6	<b>Subject index</b>
7/7	<b>Metal surcharges</b>
7/10	<b>Conditions of sale and delivery</b>

## Appendix

### Certificates of suitability (approvals)








#### Overview

Many of the products in this catalog fulfill requirements, e.g. for UL, CSA or FM and are labeled with the corresponding approval designation.

All of the certificates of suitability, approvals, certificates, declarations of conformity, test certificates, e.g. CE, UL, Safety Integrated etc. have been performed with the associated system components as they are described in the Catalogs and Configuration Manuals.

The certificates are only valid if the products are used with the described system components, are installed according to the Installation Guidelines and used for their intended purpose.





In other cases, the vendor of these products is responsible for arranging for the issue of new certificates.

Test code	Tested by	Device series/ Component	Test standard	Product category/ File No.		
<b>UL: Underwriters Laboratories</b> Independent public testing body in North America						
	UL according to UL standard	SINUMERIK	Standard UL 508, CSA C22.2 No. 142	NRAQ/7.E164110 NRAQ/7.E217227		
		SIMOTION	Standard UL 508, CSA C22.2 No. 142	NRAQ/7.E164110		
	UL according to CSA standard	SINAMICS	Standard UL 508, 508C, 61800-5-1 CSA C22.2 No. 142, 274	NRAQ/7.E164110, NMMS/2/7/8.E192450, NMMS/2/7/8.E203250, NMMS/7.E214113, NMMS/7.E253831		
				NMMS/2/7/8.E121068 NMMS/7.E355661 NMMS/7.E323473		
	UL according to UL and CSA standards					
	UL according to UL standard	SIMODRIVE	Standard UL 508C, CSA C22.2 No. 274	NMMS/2/7/8.E192450 NMMS/7.E214113		
	UL according to CSA standard	SIMOTICS	Standard UL 1004-1, 1004-6, 1004-8, CSA C22.2 No. 100	PRGY2/8.E227215 PRHZ2/8.E93429 PRHJ2/8.E342747 PRGY2/8.E253922 PRHZ2/8.E342746		
	UL according to UL and CSA standards	Line/motor reactors	Standard UL 508, 506, 5085-1, 5085-2, 1561, CSA C22.2 No. 14, 47, 66.1-06, 66.2-06	XQNX2/8.E257859 NMTR2/8.E219022 NMMS2/8.E333628 XPTQ2/8.E257852 XPTQ2/8.E103521 NMMS2/8.E224872 XPTQ2/8.E354316 XPTQ2/8.E198309 XQNX2/8.E475972		
	Line filters, dv/dt filters, sine-wave filters		UL 1283, CSA C22.2 No. 8	FOKY2/8.E70122		
	Resistors		UL 508, 508C, CSA C22.2 No. 14, 274	NMTR2/8.E224314 NMMS2/8.E192450 NMTR2/8.E221095 NMTR2/8.E226619		
<b>TUV: TÜV Rheinland of North America Inc.</b> Independent public testing body in North America, Nationally Recognized Testing Laboratory (NRTL)						
<b>TÜV: TÜV SÜD Product Service</b> Independent public testing body in Germany, Nationally Recognized Testing Laboratory (NRTL) for North America						
	TUV according to UL and CSA standards	SINAMICS	NRTL listing according to standard UL 508C	U7V 12 06 20078 013 U7 11 04 20078 009 U7 11 04 20078 010 U7 11 04 20078 011		
				SIMOTION	NRTL listing according to standard UL 508	U7V 13 03 20078 01
				SIMODRIVE	NRTL listing according to standard UL 508C, CSA C22.2. No. 14	CU 72090702
	Motion Control Encoder		NRTL listing according to UL 61010-1 CSA C22.2 No. 61010-1	U8V 10 06 20196 024		



## Certificates of suitability (approvals)

## Overview (continued)

Test code	Tested by	Device series/ Component	Test standard	Product category/ File No.
<b>CSA: Canadian Standards Association</b> Independent public testing body in Canada				
	CSA according to CSA standard	SINUMERIK	Standard CSA C22.2 No. 142	2252-01 : LR 102527
<b>FMRC: Factory Mutual Research Corporation</b> Independent public testing body in North America				
	FM according to FM standard	SINUMERIK	Standard FMRC 3600, FMRC 3611, FMRC 3810, ANSI/ISA S82.02.1	–
<b>EAC: Ivanovo-Certificate</b> Independent public testing body in the Russian Federation				
	EAC in accordance with the EAC Directive	SINAMICS SINUMERIK SIMOTION	Standard IEC 61800-5-1/-2, IEC 61800-3	–
<b>RCM: Australian Communications and Media Authority</b> Independent public testing body in Australia				
	RCM according to EMC standard	SINAMICS SINUMERIK SIMOTION	Standard IEC AS 61800-3, EN 61800-3	–
<b>BIA</b> Federal Institute for Occupational Safety				
–	Functional safety	SINAMICS SINUMERIK SIMOTION	Standard EN 61800-5-2	–
<b>TÜV SÜD Rail</b>				
–	Functional safety	SINAMICS SINUMERIK SIMOTION	Standard EN 61800-5-2	–

More information about certificates can be found online at:  
<https://support.industry.siemens.com/cs/ww/en/ps/cert>

## Appendix

### Software licenses

#### Overview

##### Software types

Software requiring a license is categorized into types. The following software types have been defined:

- Engineering software
- Runtime software

##### Engineering software

This includes all software products for creating (engineering) user software, e.g. for configuring, programming, parameterizing, testing, commissioning or servicing.

Data generated with engineering software and executable programs can be duplicated for your own use or for use by third-parties free-of-charge.

##### Runtime software

This includes all software products required for plant/machine operation, e.g. operating system, basic system, system expansions, drivers, etc.

The duplication of the runtime software and executable programs created with the runtime software for your own use or for use by third-parties is subject to a charge.

You can find information about license fees according to use in the ordering data (e.g. in the catalog). Examples of categories of use include per CPU, per installation, per channel, per instance, per axis, per control loop, per variable, etc.

Information about extended rights of use for parameterization/configuration tools supplied as integral components of the scope of delivery can be found in the readme file supplied with the relevant product(s).

##### License types

Siemens Industry Automation & Drive Technologies offers various types of software license:

- Floating license
- Single license
- Rental license
- Rental floating license
- Trial license
- Demo license
- Demo floating license

##### Floating license

The software may be installed for internal use on any number of devices by the licensee. Only the concurrent user is licensed. The concurrent user is the person using the program. Use begins when the software is started. A license is required for each concurrent user.

##### Single license

Unlike the floating license, a single license permits only one installation of the software per license.

The type of use licensed is specified in the ordering data and in the Certificate of License (CoL). Types of use include for example per instance, per axis, per channel, etc.

One single license is required for each type of use defined.

##### Rental license

A rental license supports the "sporadic use" of engineering software. Once the license key has been installed, the software can be used for a specific period of time (the operating hours do not have to be consecutive).

One license is required for each installation of the software.

##### Rental floating license

The rental floating license corresponds to the rental license, except that a license is not required for each installation of the software. Rather, one license is required per object (for example, user or device).

##### Trial license

A trial license supports "short-term use" of the software in a non-productive context, e.g. for testing and evaluation purposes. It can be transferred to another license.

##### Demo license

The demo license support the "sporadic use" of engineering software in a non-productive context, for example, use for testing and evaluation purposes. It can be transferred to another license. After the installation of the license key, the software can be operated for a specific period of time, whereby usage can be interrupted as often as required.

One license is required per installation of the software.

##### Demo floating license

The demo floating license corresponds to the demo license, except that a license is not required for each installation of the software. Rather, one license is required per object (for example, user or device).

##### Certificate of License (CoL)

The CoL is the licensee's proof that the use of the software has been licensed by Siemens. A CoL is required for every type of use and must be kept in a safe place.

##### Downgrading

The licensee is permitted to use the software or an earlier version/release of the software, provided that the licensee owns such a version/release and its use is technically feasible.

##### Delivery versions

Software is constantly being updated. The following delivery versions

- PowerPack
- Upgrade

can be used to access updates.

Existing bug fixes are supplied with the ServicePack version.

##### PowerPack

PowerPacks can be used to upgrade to more powerful software. The licensee receives a new license agreement and CoL (Certificate of License) with the PowerPack. This CoL, together with the CoL for the original product, proves that the new software is licensed.

A separate PowerPack must be purchased for each original license of the software to be replaced.

**Overview** (continued)**Upgrade**

An upgrade permits the use of a new version of the software on the condition that a license for a previous version of the product is already held.

The licensee receives a new license agreement and CoL with the upgrade. This CoL, together with the CoL for the previous product, proves that the new version is licensed.

A separate upgrade must be purchased for each original license of the software to be upgraded.

**ServicePack**

ServicePacks are used to debug existing products. ServicePacks may be duplicated for use as prescribed according to the number of existing original licenses.

**License key**

Siemens Industry Automation & Drive Technologies supplies software products with and without license keys.

The license key serves as an electronic license stamp and is also the "switch" for activating the software (floating license, rental license, etc.).

The complete installation of software products requiring license keys includes the program to be licensed (the software) and the license key (which represents the license).

**Software Update Service (SUS)**

As part of the SUS contract, all software updates for the respective product are made available to you free of charge for a period of one year from the invoice date. The contract will automatically be extended for one year if it is not canceled three months before it expires.

The possession of the current version of the respective software is a basic condition for entering into an SUS contract.

You can download explanations concerning license conditions from [www.siemens.com/automation/salesmaterial-as/catalog/en/terms\\_of\\_trade\\_en.pdf](http://www.siemens.com/automation/salesmaterial-as/catalog/en/terms_of_trade_en.pdf)

# Appendix

## Subject index

	Page		Page
<b>A</b>			
Accessories .....	1/13	OCC .....	1/8, 4/5
Applications .....	6/11	One Button Tuning .....	1/8
Approvals (certificates of suitability) .....	7/2	One Cable Connection .....	1/8, 4/5
<b>B</b>			
Braking resistors, external .....	2/11	Online Services .....	6/3
<b>C</b>			
CA 01 .....	5/2, 6/3	Online Support .....	6/8
Catalog CA 01 .....	5/2, 6/3	Order overview .....	1/12
Certificates of suitability (approvals) .....	7/2	Overcurrent protective devices .....	2/10
Characteristic curves .....	3/11, 3/13, 3/15	<b>P</b>	
Conditions of delivery .....	7/10	Partner at Siemens .....	6/2
Conditions of sale and delivery .....	7/10	Platform concept .....	1/5
Connection overview .....	1/11	PROFINET patch cable .....	2/6
Connection systems MOTION-CONNECT .....	4/1	PROFINET .....	1/10
Connection technology .....	1/8	<b>Q</b>	
<b>D</b>			
DC link components .....	2/11	Quality management according to EN ISO 9001 .....	1/5
Documentation .....	6/14	<b>R</b>	
Download Center .....	6/4	Recommended line-side power components .....	2/10
Drive selection .....	1/6	<b>S</b>	
Drive Technology Configurator .....	5/2	Safety Integrated .....	1/9
Drives Options Partners .....	6/12	Security information .....	5/1
<b>E</b>			
Energy management process .....	1/3	Services and documentation .....	6/1
Engineering tools .....	5/1	Servo drive system SINAMICS S210, overview .....	1/7, 1/12
External braking resistors .....	2/11	Shaft sealing ring .....	3/3
Fuses .....	2/10	SIMATIC S7-1500 .....	1/9
<b>I</b>			
IDS – Integration at its very best .....	1/5	SIMOTICS S-1FK2 servomotors .....	3/1
Industry Mall .....	6/3	SINAMICS as part of the Siemens modular automation system .....	1/3
Industry Services .....	6/5	SINAMICS drive family .....	1/2
Information and Download Center .....	6/4	SINAMICS S210 servo drive .....	2/1
Integration in automation .....	1/2	SINAMICS S210 servo drive system, overview .....	1/7, 1/12
Interactive Catalog CA 01 .....	5/2, 6/3	SINAMICS S210 starter kit .....	1/14
<b>L</b>			
Length code for MOTION-CONNECT cables .....	4/8	SINAMICS S210 training case .....	6/10
Line filters .....	2/10	SINAMICS SD card memory card .....	2/6, 2/12
Line-side components .....	2/10	SINAMICS selection guide – typical applications .....	1/6
<b>M</b>			
Memory card SINAMICS SD card .....	2/6, 2/12	SINAMICS web server .....	5/3
Metal surcharges .....	7/7	SITRAIN – Training for Industry .....	6/9
Mobile Media .....	6/4	Social and Mobile Media .....	6/4
MOTION-CONNECT connection systems .....	4/1	Software licenses .....	7/4
mySupport documentation .....	6/13	Supplementary system components .....	2/12
<b>O</b>			
<b>T</b>			
<b>V</b>			
<b>W</b>			
		System overview .....	1/1
		The SINAMICS drive family .....	1/2
		Totally Integrated Automation .....	1/2
		Training .....	6/9
		Typical applications – SINAMICS selection guide .....	1/6
		Web server .....	1/8, 5/3

## Explanation of the raw material/metal surcharges <sup>1)</sup>

### Surcharge calculation

To compensate for variations in the price of the raw materials silver, copper, aluminum, lead, gold, dysprosium <sup>2)</sup> and/or neodym <sup>2)</sup>, surcharges are calculated on a daily basis using the so-called metal factor for products containing these raw materials. A surcharge for the respective raw material is calculated as a supplement to the price of a product if the basic official price of the raw material in question is exceeded.

The surcharges are calculated in accordance with the following criteria:

- Basic official price of the raw material  
Basic official price from the day prior to receipt of the order or prior to release order (daily price) for <sup>3)</sup>  
- Silver (sales price, processed)  
- Gold (sales price, processed)  
and for <sup>4)</sup>  
- Copper (lower DEL notation + 1 %)  
- Aluminum (aluminum in cables)  
- Lead (lead in cables)
- Metal factor of the products  
Certain products are displayed with a metal factor. The metal factor determines the official price (for those raw materials concerned) as of which the metal surcharges are applied and the calculation method used (weight or percentage method). An exact explanation is given below.

### Structure of the metal factor

The metal factor consists of several digits; the first digit indicates whether the percentage method of calculation refers to the list price or a possible discounted price (customer net price) (L = list price / N = customer net price).

The remaining digits indicate the method of calculation used for the respective raw material. If no surcharge is added for a raw material, a "-" is used.

1st digit	List or customer net price using the percentage method
2nd digit	for silver (AG)
3rd digit	for copper (CU)
4th digit	for aluminum (AL)
5th digit	for lead (PB)
6th digit	for gold (AU)
7th digit	for dysprosium (Dy) <sup>2)</sup>
8th digit	for neodym (Nd) <sup>2)</sup>

### Weight method

The weight method uses the basic official price, the daily price and the raw material weight. In order to calculate the surcharge, the basic official price must be subtracted from the daily price. The difference is then multiplied by the raw material weight.

The basic official price can be found in the table below using the number (1 to 9) of the respective digit of the metal factor. The raw material weight can be found in the respective product descriptions.

### Percentage method

Use of the percentage method is indicated by the letters A-Z at the respective digit of the metal factor.

The surcharge is increased - dependent on the deviation of the daily price compared with the basic official price - using the percentage method in "steps" and consequently offers surcharges that remain constant within the framework of this "step range". A higher percentage rate is charged for each new step. The respective percentage level can be found in the table below.

### Metal factor examples

<b>L E A - - - - -</b>	<ul style="list-style-type: none"> <li>Basis for % surcharge: List price</li> <li>Silver Basis 150 €, Step 50 €, 0.5 %</li> <li>Copper Basis 150 €, Step 50 €, 0.1 %</li> <li>No surcharge for aluminum</li> <li>No surcharge for lead</li> <li>No surcharge for gold</li> <li>No surcharge for dysprosium</li> <li>No surcharge for neodym</li> </ul>
<b>N - A 6 - - - - -</b>	<ul style="list-style-type: none"> <li>Basis for % surcharge: Customer net price</li> <li>No surcharge for silver</li> <li>Copper Basis 150 €, Step 50 €, 0.1 %</li> <li>Aluminum acc. to weight, basic offic. price 225 €</li> <li>No surcharge for lead</li> <li>No surcharge for gold</li> <li>No surcharge for dysprosium</li> <li>No surcharge for neodym</li> </ul>
<b>- - 3 - - - - -</b>	<ul style="list-style-type: none"> <li>No basis necessary</li> <li>No surcharge for silver</li> <li>Copper acc. to weight, basic official price 150 €</li> <li>No surcharge for aluminum</li> <li>No surcharge for lead</li> <li>No surcharge for gold</li> <li>No surcharge for dysprosium</li> <li>No surcharge for neodym</li> </ul>

<sup>1)</sup> Refer to the separate explanation on the next page regarding the raw materials dysprosium and neodym (= rare earths).

<sup>2)</sup> For a different method of calculation, refer to the separate explanation for these raw materials on the next page.

<sup>3)</sup> Source: Umicore, Hanau ([www.metalsmanagement.umicore.com](http://www.metalsmanagement.umicore.com)).

<sup>4)</sup> Source: Schutzvereinigung DEL-Notiz e.V. ([www.del-notiz.org](http://www.del-notiz.org)).

## Appendix

### Metal surcharges

#### Explanation of the raw material/metal surcharges for dysprosium and neodym (rare earths)

##### Surcharge calculation

To compensate for variations in the price of the raw materials silver <sup>1)</sup>, copper <sup>1)</sup>, aluminum <sup>1)</sup>, lead <sup>1)</sup>, gold <sup>1)</sup>, dysprosium and/or neodym, surcharges are calculated on a daily basis using the so-called metal factor for products containing these raw materials. The surcharge for dysprosium and neodym is calculated as a supplement to the price of a product if the basic official price of the raw material in question is exceeded.

The surcharge is calculated in accordance with the following criteria:

- Basic official price of the raw material <sup>2)</sup>  
Three-month basic average price (see below) in the period before the quarter in which the order was received or the release order took place (= average official price) for
  - dysprosium (Dy metal, 99 % min. FOB China; USD/kg)
  - neodym (Nd metal, 99 % min. FOB China; USD/kg)
- Metal factor of the products  
Certain products are displayed with a metal factor. The metal factor indicates (for those raw materials concerned) the basic official price as of which the surcharges for dysprosium and neodym are calculated using the weight method. An exact explanation of the metal factor is given below.

##### Three-month average price

The prices of rare earths vary according to the foreign currency, and there is no freely accessible stock exchange listing. This makes it more difficult for all parties involved to monitor changes in price. In order to avoid continuous adjustment of the surcharges, but to still ensure fair, transparent pricing, an average price is calculated over a three-month period using the average monthly foreign exchange rate from USD to EUR (source: European Central Bank). Since not all facts are immediately available at the start of each month, a one-month buffer is allowed before the new average price applies.

Examples of calculation of the average official price:

Period for calculation of the average price:	Period during which the order/release order is effected and the average price applies:
Sep 2012 - Nov 2012	Q1 in 2013 (Jan - Mar)
Dec 2012 - Feb 2013	Q2 in 2013 (Apr - Jun)
Mar 2013 - May 2013	Q3 in 2013 (Jul - Sep)
Jun 2013 - Aug 2013	Q4 in 2013 (Oct - Dec)

##### Structure of the metal factor

The metal factor consists of several digits; the first digit is not relevant to the calculation of dysprosium and neodym.

The remaining digits indicate the method of calculation used for the respective raw material. If no surcharge is added for a raw material, a "-" is used.

1st digit	List or customer net price using the percentage method
2nd digit	for silver (AG) <sup>1)</sup>
3rd digit	for copper (CU) <sup>1)</sup>
4th digit	for aluminum (AL) <sup>1)</sup>
5th digit	for lead (PB) <sup>1)</sup>
6th digit	for gold (AU) <sup>1)</sup>
7th digit	for dysprosium (Dy)
8th digit	for neodym (Nd)

##### Weight method

The weight method uses the basic official price, the average price and the raw material weight. In order to calculate the surcharge, the basic official price must be subtracted from the average price. The difference is then multiplied by the raw material weight.

The basic official price can be found in the table below using the number (1 to 9) of the respective digit of the metal factor. Your Sales contact can inform you of the raw material weight.

##### Metal factor examples

-----71	No basis necessary
↑	No surcharge for silver
↑	No surcharge for copper
↑	No surcharge for aluminum
↑	No surcharge for lead
↑	No surcharge for gold
↑	Dysprosium acc. to weight, basic official price 300 €
↑	Neodym acc. to weight, basic official price 50 €

<sup>1)</sup> For a different method of calculation, refer to the separate explanation for these raw materials on the previous page.

<sup>2)</sup> Source: Asian Metal Ltd ([www.asianmetal.com](http://www.asianmetal.com))

## Values of the metal factor

Percentage method	Basic official price in €	Step range in €	% surcharge 1st step	% surcharge 2nd step	% surcharge 3rd step	% surcharge 4th step	% surcharge per additional step
			Price in €	Price in €	Price in €	Price in €	
			150.01 - 200.00	200.01 - 250.00	250.01 - 300.00	300.01 - 350.00	
A	150	50	0.1	0.2	0.3	0.4	0.1
B	150	50	0.2	0.4	0.6	0.8	0.2
C	150	50	0.3	0.6	0.9	1.2	0.3
D	150	50	0.4	0.8	1.2	1.6	0.4
E	150	50	0.5	1.0	1.5	2.0	0.5
F	150	50	0.6	1.2	1.8	2.4	0.6
G	150	50	1.0	2.0	3.0	4.0	1.0
H	150	50	1.2	2.4	3.6	4.8	1.2
I	150	50	1.6	3.2	4.8	6.4	1.6
J	150	50	1.8	3.6	5.4	7.2	1.8
			175.01 - 225.00	225.01 - 275.00	275.01 - 325.00	325.01 - 375.00	
O	175	50	0.1	0.2	0.3	0.4	0.1
P	175	50	0.2	0.4	0.6	0.8	0.2
R	175	50	0.5	1.0	1.5	2.0	0.5
			225.01 - 275.00	275.01 - 325.00	325.01 - 375.00	375.01 - 425.00	
S	225	50	0.2	0.4	0.6	0.8	0.2
U	225	50	1.0	2.0	3.0	4.0	1.0
V	225	50	1.0	1.5	2.0	3.0	1.0
W	225	50	1.2	2.5	3.5	4.5	1.0
			150.01 - 175.00	175.01 - 200.00	200.01 - 225.00	225.01 - 250.00	
Y	150	25	0.3	0.6	0.9	1.2	0.3
			400.01 - 425.00	425.01 - 450.00	450.01 - 475.00	475.01 - 500.00	
Z	400	25	0.1	0.2	0.3	0.4	0.1
<b>Price basis (1st digit)</b>							
L	Calculation based on the list price						
N	Calculation based on the customer net price (discounted list price)						
<b>Weight method</b>	<b>Basic official price in €</b>						
1	50	Calculation based on raw material weight					
2	100						
3	150						
4	175						
5	200						
6	225						
7	300						
8	400						
9	555						
<b>Miscellaneous</b>							
-	No metal surcharge						

## Appendix

### Conditions of sale and delivery

#### 1. General Provisions

By using this catalog you can acquire hardware and software products described therein from Siemens AG subject to the following Terms and Conditions of Sale and Delivery (hereinafter referred to as "T&C"). Please note that the scope, the quality and the conditions for supplies and services, including software products, by any Siemens entity having a registered office outside Germany, shall be subject exclusively to the General Terms and Conditions of the respective Siemens entity. The following T&C apply exclusively for orders placed with Siemens Aktiengesellschaft, Germany.

##### 1.1 For customers with a seat or registered office in Germany

For customers with a seat or registered office in Germany, the following applies subordinate to the T&C:

- the "General Terms of Payment"<sup>1)</sup> and,
- for software products, the "General License Conditions for Software Products for Automation and Drives for Customers with a Seat or Registered Office in Germany"<sup>1)</sup> and,
- for other supplies and services, the "General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry"<sup>1)</sup>.

##### 1.2 For customers with a seat or registered office outside Germany

For customers with a seat or registered office outside Germany, the following applies subordinate to the T&C:

- the "General Terms of Payment"<sup>1)</sup> and,
- for software products, the "General License Conditions for Software Products for Automation and Drives for Customers with a Seat or Registered Office outside of Germany"<sup>1)</sup> and
- for other supplies and/or services, the "General Conditions for Supplies of Siemens Industry for Customers with a Seat or Registered Office outside of Germany"<sup>1)</sup>.

#### 2. Prices

The prices are in € (Euro) ex point of delivery, exclusive of packaging.

The sales tax (value added tax) is not included in the prices. It shall be charged separately at the respective rate according to the applicable statutory legal regulations.

Prices are subject to change without prior notice. We will charge the prices valid at the time of delivery.

To compensate for variations in the price of raw materials (e.g. silver, copper, aluminum, lead, gold, dysprosium and neodym), surcharges are calculated on a daily basis using the so-called metal factor for products containing these raw materials. A surcharge for the respective raw material is calculated as a supplement to the price of a product if the basic official price of the raw material in question is exceeded.

The metal factor of a product indicates the basic official price (for those raw materials concerned) as of which the surcharges on the price of the product are applied, and with what method of calculation.

You will find a detailed explanation of the metal factor on the page headed "Metal surcharges".

To calculate the surcharge (except in the cases of dysprosium and neodym), the official price from the day prior to that on which the order was received or the release order was effected is used.

To calculate the surcharge applicable to dysprosium and neodym ("rare earths"), the corresponding three-month basic average price in the quarter prior to that in which the order was received or the release order was effected is used with a one-month buffer (details on the calculation can be found in the explanation of the metal factor).

#### 3. Additional Terms and Conditions

The dimensions are in mm. In Germany, according to the German law on units in measuring technology, data in inches apply only to devices for export.

Illustrations are not binding.

Insofar as there are no remarks on the individual pages of this catalog – especially with regard to data, dimensions and weights given – these are subject to change without prior notice.

#### 4. Export regulations

We shall not be obligated to fulfill any agreement if such fulfillment is prevented by any impediments arising out of national or international foreign trade or customs requirements or any embargoes and/or other sanctions.

Export of goods listed in this catalog may be subject to licensing requirements. We will indicate in the delivery details whether licenses are required under German, European and US export lists. Goods labeled with "AL" not equal to "N" are subject to European or German export authorization when being exported out of the EU. Goods labeled with "ECCN" not equal to "N" are subject to US re-export authorization.

The export indications can be viewed in advance in the description of the respective goods on the Industry Mall, our online catalog system. Only the export labels "AL" and "ECCN" indicated on order confirmations, delivery notes and invoices are authoritative.

Even without a label, or with label "AL:N" or "ECCN:N", authorization may be required i.a. due to the final disposition and intended use of goods.

If you transfer goods (hardware and/or software and/or technology as well as corresponding documentation, regardless of the mode of provision) delivered by us or works and services (including all kinds of technical support) performed by us to a third party worldwide, you must comply with all applicable national and international (re-)export control regulations.

If required for the purpose of conducting export control checks, you (upon request by us) shall promptly provide us with all information pertaining to the particular end customer, final disposition and intended use of goods delivered by us respectively works and services provided by us, as well as to any export control restrictions existing in this relation.

The products listed in this catalog may be subject to European/German and/or US export regulations. Any export requiring approval is therefore subject to authorization by the relevant authorities.

Errors excepted and subject to change without prior notice.

<sup>1)</sup> The text of the Terms and Conditions of Siemens AG can be downloaded at:  
[www.siemens.com/automation/salesmaterial-as/catalog/en/terms\\_of\\_trade\\_en.pdf](http://www.siemens.com/automation/salesmaterial-as/catalog/en/terms_of_trade_en.pdf)



Further information can be obtained from our branch offices listed at [www.siemens.com/automation-contact](http://www.siemens.com/automation-contact)

<b>Interactive Catalog on DVD</b>	<i>Catalog</i>	<b>Process Instrumentation and Analytics</b>	<i>Catalog</i>
Products for Automation and Drives	<b>CA 01</b>	<i>Digital: Field Instruments for Process Automation</i>	FI 01
<b>Building Control</b>		<i>Digital: Display Recorders SIREC D</i>	MP 20
GAMMA Building Control	ET G1	<i>Digital: SIPART Controllers and Software</i>	MP 31
<b>Drive Systems</b>		Products for Weighing Technology	WT 10
SINAMICS G130 Drive Converter Chassis Units	D 11	<i>Digital: Process Analytical Instruments</i>	AP 01
SINAMICS G150 Drive Converter Cabinet Units		<i>Digital: Process Analytics, Components for Continuous Emission Monitoring</i>	AP 11
SINAMICS GM150, SINAMICS SM150 Medium-Voltage Converters	D 12	<b>Low-Voltage Power Distribution and Electrical Installation Technology</b>	
<i>Digital: SINAMICS PERFECT HARMONY GH180 Medium-Voltage Air-Cooled Drives (Germany)</i>	D 15.1	SENTRON · SIVACON · ALPHA Protection, Switching, Measuring and Monitoring Devices, Switchboards and Distribution Systems	LV 10
SINAMICS G180 Converters – Compact Units, Cabinet Systems, Cabinet Units Air-Cooled and Liquid-Cooled	D 18.1	Standards-Compliant Components for Photovoltaic Plants	LV 11
SINAMICS S120 Chassis Format Units and Cabinet Modules	D 21.3	Electrical Components for the Railway Industry	LV 12
SINAMICS S150 Converter Cabinet Units		Power Monitoring Made Simple	LV 14
SINAMICS S120 and SIMOTICS	D 21.4	Components for Industrial Control Panels according to UL Standards	LV 16
SINAMICS DCM DC Converter, Control Module	D 23.1	3WT Air Circuit Breakers up to 4000 A	LV 35
SINAMICS Inverters for Single-Axis Drives · Built-In Units	D 31.1	3VT Molded Case Circuit Breakers up to 1600 A	LV 36
SINAMICS Inverters for Single-Axis Drives · Distributed Inverters	D 31.2	<i>Digital: SIVACON System Cubicles, System Lighting and System Air-Conditioning</i>	LV 50
SINAMICS G120P and SINAMICS G120P Cabinet pump, fan, compressor converters	D 35	<i>Digital: ALPHA Distribution Systems</i>	LV 51
LOHER VARIO High Voltage Motors Flameproof, Type Series 1PS4, 1PS5, 1MV4 and 1MV5 Frame Size 355 to 1000, Power Range 80 to 7100 kW	D 83.2	ALPHA FIX Terminal Blocks	LV 52
Three-Phase Induction Motors	D 84.1	SIVACON S4 Power Distribution Boards	LV 56
SIMOTICS HV, SIMOTICS TN		SIVACON 8PS Busbar Trunking Systems	LV 70
High Voltage Three-phase Induction Motors	D 84.9	<i>Digital: DELTA Switches and Socket Outlets</i>	ET D1
SIMOTICS HV Series A-compact PLUS		Vacuum Switching Technology and Components for Medium Voltage	HG 11.01
<i>Digital: Modular Industrial Generators SIGENTICS M</i>	D 85.1	<b>Motion Control</b>	
Three-Phase Induction Motors SIMOTICS HV, Series H-compact	D 86.1	SINUMERIK 840 Equipment for Machine Tools	NC 62
Synchronous Motors with Permanent-Magnet Technology, HT-direct	D 86.2	SINUMERIK 808 Equipment for Machine Tools	NC 81.1
DC Motors	DA 12	SINUMERIK 828 Equipment for Machine Tools	NC 82
SIMOREG DC MASTER 6RA70 Digital Chassis Converters	DA 21.1	SIMOTION Equipment for Production Machines	PM 21
SIMOREG K 6RA22 Analog Chassis Converters	DA 21.2	<i>Digital: Drive and Control Components for Cranes</i>	CR 1
<i>Digital: SIMOREG DC MASTER 6RM70 Digital Converter Cabinet Units</i>	DA 22	<b>Power Supply</b>	
SIMOVERT PM Modular Converter Systems	DA 45	SITOP Power supply	KT 10.1
MICROMASTER 420/430/440 Inverters	DA 51.2	<b>Safety Integrated</b>	
MICROMASTER 411/COMBIMASTER 411	DA 51.3	Safety Technology for Factory Automation	SI 10
<u>Low-Voltage Three-Phase-Motors</u>		<b>SIMATIC HMI / PC-based Automation</b>	
SIMOTOCS S-1FG1 Servo geared motors	D 41	Human Machine Interface Systems/ PC-based Automation	ST 80/ ST PC
SIMOTICS Low-Voltage Motors	D 81.1	<b>SIMATIC Ident</b>	
SIMOTICS FD Low-Voltage Motors	D 81.8	Industrial Identification Systems	ID 10
LOHER Low-Voltage Motors	D 83.1	<b>SIMATIC Industrial Automation Systems</b>	
<i>Digital: MOTOX Geared Motors</i>	D 87.1	Products for Totally Integrated Automation	ST 70
SIMOGEAR Geared Motors	MD 50.1	SIMATIC PCS 7 Process Control System System components	ST PCS 7
SIMOGEAR Electric-monorail geared motors Light-load and heavy-load applications	MD 50.8	SIMATIC PCS 7 Process Control System Technology components	ST PCS 7 T
SIMOGEAR Gearboxes with adapter	MD 50.11	Add-ons for the SIMATIC PCS 7 Process Control System	ST PCS 7 AO
<u>Mechanical Driving Machines</u>		SIMATIC S7-400 advanced controller	ST 400
FLENDER Standard Couplings	MD 10.1	<b>SIMATIC NET</b>	
FLENDER High Performance Couplings	MD 10.2	Industrial Communication	IK PI
FLENDER Backlash-free Couplings	MD 10.3	<b>SIRIUS Industrial Controls</b>	
FLENDER SIP Standard industrial planetary gear units	MD 31.1	<i>Digital: SIRIUS Industrial Controls</i>	IC 10

*Digital: These catalogs are only available as a PDF.***Information and Download Center**

Digital versions of the catalogs are available on the Internet at:

[www.siemens.com/industry/infocenter](http://www.siemens.com/industry/infocenter)

There you'll find additional catalogs in other languages.

Please note the section "Downloading catalogs" on page "Online services" in the appendix of this catalog.

## Get more information

SINAMICS S210 servo drive system:  
[www.siemens.com/sinamics-s210](http://www.siemens.com/sinamics-s210)

SIMOTICS electric motors:  
[www.siemens.com/simotics](http://www.siemens.com/simotics)

Motion Control Systems and Solutions for production machine and machine tool equipment:  
[www.siemens.com/motioncontrol](http://www.siemens.com/motioncontrol)

Local partners worldwide:  
[www.siemens.com/automation-contact](http://www.siemens.com/automation-contact)

Siemens AG  
Digital Factory Division  
Motion Control  
Postfach 31 80  
91050 ERLANGEN  
GERMANY

© Siemens AG 2017  
Subject to change without prior notice  
PDF (E86060-K5532-A101-A1-7600)  
V6.MKKATA.GMC.171  
KG 0118 HOF 84 En  
Produced in Germany

The information provided in this catalog contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract. Availability and technical specifications are subject to change without notice.

All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.

## Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, systems, machines and networks.

In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial security concept. Siemens' products and solutions constitute one element of such a concept.

Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place.

For additional information on industrial security measures that may be implemented, please visit  
<https://www.siemens.com/industrialsecurity>

Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats.

To stay informed about product updates, subscribe to the Siemens Industrial Security RSS Feed under  
<https://www.siemens.com/industrialsecurity>

Discover the  
advantages of  
Integrated Drive  
Systems at a glance

