

## Related catalogs

Industrial ControlsIC 10SIRIUSPDF (E86060-K1010-A101-A9-7600)		Motion Control System SIMOTION Equipment for Production Machines E86060-K4921-A101-A4-7600	PM 21	
SIMATICST 70Products for Totally Integrated AutomationST 70PDF (E86060-K4670-A101-B7-7600)ST 70	EXAMPLE Finduces for Focalizes for Focalizes for Focalizes for	SITRAIN Training for Industry www.siemens.com/sitrain		
SIMATIC ST PCS 7 SIMATIC PCS 7 Process Control System Vol. 1: System components E86060-K4678-A111-C5-7600		Products for Automation and Drives Interactive Catalog Download www.siemens.com/ca01download	CA 01	SIMS -
SIMATIC HMI / PC-based AutomationST 80/ST PCHuman Machine Interface Systems PC-based AutomationST 80/ST PCE86060-K4680-A101-C6-7600E86060-K4680-A101-C6-7600		Industry Mall Information and Ordering Platform on the Internet: www.siemens.com/industrymall		







# **TIA Selection Tool**

The smart configurator for the entire Siemens automation portfolio



## Prime reasons for the TIA Selection Tool



## Quick, easy and secure

Components can be selected, configured and ordered quickly, easily and securely from the Siemens automation portfolio



Intelligent

Intelligent selection wizards check the compatibility of the configured components and enable error-free ordering




Clear

Required modules, devices and networks are automatically generated and clearly compared to one another



## **Time-saving**

Time savings of 80% in design – thanks to ease of use and intelligent support



The TIA Selection Tool is a completely paperless solution. Download it now: www.siemens.com/tst

For more information, scan the QR code



© Siemens 2019

# **SITOP Power supplies**

SITOP



#### Catalog KT 10.1 · 2019/2020

Supersedes: Catalog KT 10.1 · 2017/2018

Refer to the Industry Mall for current updates of this catalog: www.siemens.com/industrymall

The products contained in this catalog can also be found in the Interactive Catalog CA 01. Article No.: E86060-D4001-A510-D8

Please contact your local Siemens branch.

© Siemens 2019

Introduction	1
Advanced power supplies	2
Standard power supplies	3
Basic power supplies	4
SITOP in the SIMATIC Design	5
DC/DC converter	6
Special designs, special uses	7
SITOP DC UPS uninterruptible power supplies	8
Add-on modules	9
Accessories	10
Technical information and configuration	11
Appendix	12



The products and systems described in this catalog are manufactured/distributed under application of a certified quality management system in accordance with DIN EN ISO 9001 (Certified Registration No. 000656 QM08). The certificate is recognized by all IQNet countries.

# **Digital Enterprise**

The building blocks that ensure everything works together perfectly in the digital enterprise

Digitalization is already changing all areas of life and existing business models. It is placing greater pressure on industry while at the same time creating new business opportunities. Today, thanks to scalable solutions from Siemens, companies can already become a digital enterprise and ensure their competitiveness.



#### Industry faces tremendous challenges



## Reduce time-to-market

Today manufacturers have to bring products to market at an ever-increasing pace despite the growing complexity of these products. In the past, a major manufacturer would push aside a small one, but now it is a fast manufacturer that overtakes a slow one.



Boost flexibility

Consumers want customized products, but at a price they would pay for a mass-produced item. That only works if production is more flexible than ever before.



Improve quality

To ensure a high level of quality while meeting legal requirements, companies have to establish closed quality loops and enable the traceability of products.




Boost efficiency

Today the product itself needs to be sustainable and environmentally friendly, while energy efficiency in production has become a competitive advantage.



# Increase security

Increasing networking escalates the threat to production facilities of cyberattacks. Today more than ever, companies need suitable security measures.



# The digital enterprise has already become a reality

To fully benefit from all the advantages of digitalization, companies first have to achieve complete consistency of their data. Fully digitally integrated business processes, including those of suppliers, can help to create a digital representation of the entire value chain. This requires

- the integration of industrial software and automation,
- expansion of the communication networks,
- security in automation,
- and the use of business-specific industrial services.

#### MindSphere The cloud-based open IoT operating system from Siemens

With MindSphere, Siemens offers a costeffective and scalable cloud platform as a service (PaaS) for the development of applications. The platform, designed as an open operating system for the Internet of Things, makes it possible to improve the efficiency of plants by collecting and analyzing large volumes of production data.

#### **Totally Integrated Automation (TIA)** Where digitalization becomes reality

Totally Integrated Automation (TIA) ensures the seamless transition from the virtual to the real world. It already encompasses all the necessary conditions for transforming the benefits of digitalization into true added value. The data that will form the digital twin for actual production is generated from a common base.

#### **Digital Plant**

Learn more about the digital enterprise for the process industry www.siemens.com/ digitalplant

Digital Enterprise Suite Learn more about the digital enterprise for the discrete industry www.siemens.com/ digital-enterprise-suite © Siemens 2019

## Notes

© Siemens 2019

## Introduction



- SITOP power supply
- 2 Introduction

1/2

- The product range at a glance
- Efficient product selection and planning
- Customized power supplies
- Selection tables for power supplies

#### SITOP power supply

## Introduction

## Overview

#### SITOP - The heart of automation<sup>®</sup>

Thanks to their high degree of reliability, SITOP power supplies have established themselves around the world and can cope with even critical network conditions. Our complete range of power packs supplies regulated 24 volt and other output voltages. The unique range of DC UPS and add-on modules extends the power supply system: 24 V supplies are thus protected against interference from the grid and on the direct voltage side.

#### Top SITOP reliability

SITOP has proved its reliability in almost every supply system in the world. With its flexible wide range input, excellent load characteristics and all relevant certification, SITOP power packs preserve the availability of your plant. Add-on modules counteract disturbances on the DC voltage or line side. And in addition to the uninterruptible power supply, the 24 V power supplies bridge power failures in the range of seconds, minutes or hours.

Even in the event of an overload or short-circuit, the output circuit maintains the selective shutdown of the feeder and the loads continue to be supplied. Redundant power supply solutions can be configured for especially critical applications. Should a replacement be required, our global customer service ensures fast delivery: All SITOP products can be delivered from stock.

#### **Top SITOP efficiency**

Lower energy costs are a valuable competitive advantage. SITOP has an essential role to play here: The primary switched mode power supplies work extremely effectively. The SITOP PSU8200 und PSU6200 degree of efficiency is up to 95%, for example. The power loss across the entire performance range is low – even during no-load operation. This is important because power supplies are rarely operated at full load.

The SITOP PSU8600, on the other hand, captures the energy data of all outputs which are then further processed by the energy management systems. The power supply outputs can also be specifically switched off with the support of PROFlenergy, for instance during idle times. Efficiency characterizes the entire process chain: Special tools are provided for easy selection of the power supply and DC UPS, for instance, and users are given all construction data for all commonly used CAE systems along with the corresponding product documentation.

#### **Top SITOP integration**

SITOP is the benchmark in integration: The inclusion of the SITOP PSU8600 power supply system and SITOP UPS1600 DC uninterruptible power supply in Totally Integrated Automation, the TIA Portal and the new SITOP Manager at all levels saves time and costs and simplifies failsafe engineering. The S7 function blocks evaluate important diagnostic information for the SITOP selectivity modules and the new SITOP PSU6200 product line.

In order to protect PC-based automation systems from power outages, the SITOP UPS1600 can be easily integrated via USB or Ethernet. And the SITOP library for SIMATIC PCS 7 enables transparent 24 V supply in the process control system during ongoing operation. In addition to PROFINET, the SITOP PSU8600 and SITOP UPS1600 can now also communicate via OPC UA. The OPC UA server enables direct incorporation of controllers or PCs, for example, into automation applications with OPC UA clients from different manufacturers.

## Three SITOP categories for different industrial power supply requirements

#### Advanced power supplies

The switched mode power supplies in the Advanced performance class are the ideal choice for maximum reliability and functionality, as required in the process and automotive industries, in special-purpose machine manufacturing, or in harsh environments. Its overload characteristics, efficiency, and compactness mean that the SITOP PSU8200 product range meets the stringent requirements in these areas. Additionally, SITOP PSU8600 offers a power supply system with open communication for optimum integration into the world of digitalization.

#### Standard power supplies

Our standard portfolio was designed with typical industrial requirements in mind, such as those encountered in series machine production. The versatile new SITOP PSU6200 was developed on the basis of our experience with the time-proven SITOP smart product line. This new SITOP Standard offers even more efficiency, extensive diagnostic options and enhanced robustness.

#### **Basic power supplies**

From flat power supplies for distribution boards, through costeffective basic power supplies, to slim power supply units for control boxes – SITOP caters to all needs, including in the lower performance range. LOGO!Power offers you miniature power supply units in the LOGO!8 module design, for example. The extremely space-saving SITOP compact devices are ideally suited for distributed applications. And SITOP lite fulfills the main requirements for reliable primary switched-mode regulators at an affordable price.

### SITOP power supply

The product range at a glance



**SITOP inrush current limiter** Protecting your loads

Siemens KT 10.1 · 2019/2020

#### Efficient product selection and planning


#### Overview

However sophisticated the requirements are for your power supply, SITOP always provides optimal support for your planning process: from product selection to mechanical and electrical construction and project-specific plant documentation, up to engineering.

SITOP and the TIA Selection Tool make it possible to select your power supply and DC UPS faster and more directly. Moreover, you also receive the right CAD data and circuit diagram macros automatically. And parameter assignment and diagnostics of the modular SITOP PSU8600 power supply system and SITOP UPS1600 DC UPS is easy via the TIA Portal.

#### Efficiency begins with the right choice

With just a few mouse clicks, the TIA Selection Tool guides you to the optimum power supply and DC UPS for your requirements. Simply enter the relevant parameters. In the case of multiple solutions, an overview is presented with a tabular comparison of the various devices. Once you have made your selection, the resulting product list can be exported in a range of different formats to other CAE (e.g. EPLAN) or engineering systems (such as the TIA Portal) for further processing. With just one click, your selected products are transferred to the shopping cart of the Industry Mall ready for ordering. In addition, the 24 V consumer view in the TIA Selection Tool helps you to pick the right power supply for your project by automatically calculating the current demand of the chosen automation products. If required, matching redundancy and selectivity modules are also available.



24 V DC power consumer view of the TIA Selection Tool

You can find out more about the 24 V consumer view in the TIA Selection Tool here: www.siemens.com/tst

#### Everything you need for project planning

Additional information such as 3D data, circuit diagram macros according to IEC and ANSI, certificates and operating instructions are available at the click of the mouse. The engineering data can be downloaded with the help of the CAx Manager in DXF, STEP, EPLAN and eCI@ss advanced format for immediate use in your configuration planning. This not only saves you valuable time at the design stage, you also benefit from configurable manuals when creating individual project documentation with the My Documentation Manager.



CAD and CAE data in the industry image database make configuration easy  $\label{eq:capacity}$ 

CAxonline	Kontakt	
Ax - neuer Warenkorb		
1. Produktnummern 2. Forma auswähl		$\rangle$
CAx-Datenarten		
Zur Warenkrebübersicht	Zunick Weller	-

All product information is available from the CAx Download

## SITOP power supply

## Overview

Our well-proven standard power supplies cannot, of course, satisfy the requirements of every application. We make it possible for you to optimize your system to suit applicationspecific requirements.

You benefit from the expertise of large-scale production and gain maximum development security and quality.

Our customer-specific solutions are used today in many sectors of mechanical engineering, in automation technology, vehicle electronics, equipment manufacturing and in industrial instrumentation technology.

Our offer is in principle open to every application case. If we have awakened your interest or if you would like to receive further details, please contact your local Siemens representative.

#### © Siemens 2019

## SITOP power supply

## Selection tables for power supplies

Input voltage	Output current	SITOP PSU8600	SITOP PSU8200	SITOP PSU6200	SITOP smart	SITOP lite	LOGO! Power	SITOP compact	SIMATIC- Design	DC/DC- Wandler	Special design special uses
Output volta	ge 24 V DC	You will fin	nd all the tec	hnical speci	fications fo	r these pro	ducts on the	pages speci	fied below		
1-phase AC											
100 240 V	0,6 A						4/18				
	1,3 A						4/18				
	2,1 A										7/7
	2,5 A						4/18				
	3,1 A										7/7
	4 A						4/18				
	4,1 A						1,10				7/7
	6,2 A										7/7
	12,5 A										7/7
	20 A					4/4					.,,
110 220 V			2/22			4/4					
120 230 V			2/22					4/26			
or				2/0							
120 V/230 V	1,3 A			3/9				4/26	E/2		
	2 A			0.10	0/10	414		4/00	5/3		
	2,5 A			3/9	3/19	4/4		4/26	5/9		
	3 A								5/11		7/00
	3 - 52 V/ 10 A										7/28
	3,7 A			3/9				4/26			
	4 A			0,0				4/26			
	5 A		2/22, 2/27	3/11	3/19	4/4		4/20	5/6, 5/14		7/10, 7/22, 7/30
			2/22, 2/21	3/11	3/19	4/4					
	8 A		0/00 0/07	0/11	0/10	4/4			5/11		7/10
	10 A		2/22, 2/27	3/11	3/19	4/4			5/6, 5/14		7/30
	20 A		0/00	3/11	3/19						
	40 A		2/22								
1-phase DC											
12 12 V	4 A									6/4	
24 24 V	5 A									6/4	
	10 A									6/6	
48 48 V	3,5 A									6/4	
	5 A									6/4	
	10 A									6/6	
48 220 V	0,375 A									6/12	
24 110 V	2 A								5/3		
30 75,5 V	5 A									6/18	
48 110 V	2 A									6/14	
110 300 V	0,6 A						4/18	4/26			
	1,3 A						4/18	4/26			
	2,5 A						4/18	4/26			
	3,7 A							4/26			
	4 A						4/18	4/26			
120 230 V											7/28
	10 A										
	5 A										7/22
300 900 V	20 A									6/10	
	5 A				3/24						7/35
3-phasig AC					3/24						
3-phasig AC	10 A										7/18
3-phasig AC											
3-phasig AC	17 A	2/7	2/32		3/24						7/24
3-phasig AC	17 A 20 A	2/7	2/32		3/24						7/24 7/18
3-phasig AC	17 A 20 A 30 - 40 A										7/24 7/18
3-phasig AC	17 A 20 A 30 - 40 A 40 A	2/7	2/32 2/32		3/24 3/24						
3-phasig AC 400 500 V	17 A 20 A 30 - 40 A										

## SITOP power supply

Selection tables for power supplies

Input voltage	Output current	SITOP PSU8600	SITOP PSU8200	SITOP PSU6200	SITOP smart	SITOP lite	LOGO! Power	SITOP compact	SIMATIC- Design	DC/DC- Wandler	Special design special uses
Output volta 5, 12, 15, 36,	ge 48 V DC	You will fir	nd all the tec	hnical speci	ifications fo	or these pro	ducts on the	pages speci	fied below		
1-phase AC											
100 230 V	12 V/2 A							4/23			
	12 V/6,5 A							4/23			
100 240 V	5 V/3 A						4/9				
	5 V/6,3 A						4/9				
	12 V/0,9 A						4/12				
	12 V/1,9 A						4/12				
	12 V/3 A										7/4
	12 V/4,5 A						4/12				
	12 V/8,3 A										7/4
	15 V/1,9 A						4/15				.,.
	15 V/4 A						4/15				
120 230 V				3/5			1,10				
or	12 V/7 A			3/5	3/16						
120 V/230 V	12 V/12 A			3/5	5/10						
	12 V/12 A			3/3	3/16						
	2 x 15 V/				3/10						7/26
	3,5 A 48 V/5 A										7/33
1-phase DC											.,
14 32 V	12 V/15 A									6/6	
24 24 V	12 V/2,5 A									6/16	
V	12 V/2,077									6/4	
110 300 V							4/9			0/4	
110 300 V	5 V/6,3 A						4/9				
	12 V/0,9 A						4/12				
	12 V/0,9 A 12 V/1,9 A						4/12				
	12 V/1,9 A 12 V/2 A						4/12	4/23			
	12 V/2 A 12 V/4,5 A						4/12	4/23			
	12 V/4,5 A						4/12	4/23			
								4/23		6/6	
	12 V/15 A						4/45			0/0	
	15 V/1,9 A						4/15				
	15 V/4 A						4/15				
3-phase AC	101//00.1										7/10
400 500 V			0/00								7/16
	36 V/13 A		2/36								
	48 V/10 A		2/38								
	48 V/20 A 4 - 28 V/	2/7	2/38								
	20 A 4 - 28 V/	2/7									
	40 Å										
	4 - 28 V/ 4 x 5 A	2/7									
	4 - 28 V/ 4 x 10 A	2/7									

1/8

Siemens KT 10.1 · 2019/2020

© Siemens 2019

© Siemens 2019

## Advanced power supplies





2/2	Overview
2/3	SITOP PSU8600 power supply system
2/3	Introduction
2/7	3-phase, basic units 24 V DC (PSU8600)
2/12	Modular system, expansion of outputs
	(CNX8600)
2/16	Modular system, buffering
	(BUF8600 and UPS8600)
2/21	SITOP PSU8200
2/21	Introduction
2/22	1-phase, 24 V DC
2/27	1- and 2-phase, 24 V DC
2/32	3-phase, 24 V DC
2/36	3-phase, 36 V DC
2/38	3-phase, 48 V DC

#### Introduction

#### Overview


The switching power supply units in the Advanced performance class are the ideal choice for maximum reliability and functionality, as required in the process and automotive industries, in special-purpose machine manufacturing, or in harsh environments.

The SITOP PSU8200 product range meets the stringent requirements in these areas, e.g. thanks to its overload characteristics, efficiency, and compactness. Additionally, SITOP PSU8600 offers a power supply system with open communication for optimum integration in the world of digitalization.

### Advanced power supplies SITOP PSU8600 power supply system

#### Introduction

#### Overview



As a unique power supply system with network integration, SITOP PSU8600 sets new standards in industrial power supplies. It can be fully integrated into Totally Integrated Automation (TIA) and networked via OPC UA and SITOP Manager with automation systems from different manufacturers.

The comprehensive functions offer new possibilities, and the online diagnostics increase the reliability of the power supply. Voltage and current response thresholds can be set individually for each output of the power supply system, and selective monitoring of each output for overload allows fast fault location. Depending on requirements, more modules from the modular system can be added without wiring work, for example to buffer against power failures in the second, minute or hour range, or for increasing the number of outputs.

SITOP PSU8600 can be easily configured in the TIA Portal: From the product selection through the network integration to the parameter assignment.

Comprehensive diagnostic and maintenance information is available via PROFINET. It can be evaluated directly in SIMATIC S7 and visualized in SIMATIC WinCC. Remote monitoring is also possible via the integrated web server. Optimal support is also provided for energy management of plant or machines: From the acquisition of energy data from individual outputs, the specific activation and deactivation of outputs via PROFIenergy, to direct integration in power management systems.


The integrated OPC UA server also allows direct integration into automation applications with OPC UA clients made by different manufacturers, e.g. of controllers or PCs. The power supply system can be both configured and diagnosed via the open interface, e.g. via SITOP Manager.

## Benefits

- Space and cost savings through up to 36 integrated outputs with selective monitoring (no need for one or more additional selectivity modules)
- Individually parameterizable outputs (elimination of an additional power supply unit, e.g. for 5 V, 12 V or 15 V)
- Compensation for power losses can be set separately for each output
- Narrow width without lateral installation clearances
- Low temperature rise in the control cabinet due to very high efficiency
- Depending on requirements, modular expansion without wiring work (additional outputs, buffer module, UPS module)
- Reliable operation by bridging power failures in the second, minute or hour range
- Two integrated Ethernet/PROFINET ports (no external switch required)
- Integrated web server
- Integrated OPC UA server for open, multi-vendor communication
- Complete integration in TIA requires less time and reduces costs during configuration (TIA Portal) and in operation
- SIMATIC S7 function blocks for easy integration in STEP 7 user programs
- Fast integration in operator control and monitoring with WinCC faceplates
- Direct integration in SIMATIC PCS 7 via SITOP library
- Easy configuration and monitoring via SITOP Manager
- Preventive maintenance reduces downtimes
- Energy savings during breaks through targeted switching of outputs
- Easy integration in energy management systems (PROFlenergy protocol)

#### Application

SITOP PSU8600 power supply system is used as a central DC power supply in larger plants, or machines with networked automation systems. The PSU8600 can be directly integrated into the LAN infrastructure by means of the two integrated PROFINET ports.



SITOP PSU8600 power supply system

#### Introduction

#### Application (continued)

An extremely high level of reliability is achieved for the DC voltage supply by monitoring the individual DC branches for overload and bridging short-term power failures (brownouts). Complete transparency and fast fault localization are achieved by providing comprehensive diagnostic and maintenance information (e.g. load states of the outputs, phase/network failure, overtemperature) via PROFINET.

Energy-optimized operation is supported by measuring the current power and voltage values of the individual outputs as well as the individual activation and deactivation of the DC outputs via PROFlenergy during break times.

#### Desian

- SITOP PSU8600, 3-phase power supply, 24 V DC/20 A/4 x 5 A with four outputs (max. 5 Å per output) and two Ethernet/ PROFINET ports
- SITOP PSU8600, 3-phase power supply, 24 V DC/20 A with one output and two Ethernet/PROFINET ports
- SITOP PSU8600, 3-phase power supply, 24 V DC/40 A/4 x 10 A with four outputs (max. 10 A per output) and two Ethernet/PROFINET ports
- SITOP PSU8600, 3-phase power supply, 24 V DC/40 A with one output and two Ethernet/PROFINET ports

Modular system, consisting of:

- SITOP CNX8600 4 x 5 A
- (expansion module with 4 outputs, each 5 A) SITOP CNX8600 4 x 10 A
- (expansion module with 4 outputs, each 10 A)
- SITOP CNX8600 8 x 2.5 A (expansion module with 8 outputs, each 2.5 A)
- SITOP BUF8600 100 ms/40 A (buffer module with 100 ms at 40 A)
- SITOP BUF8600 300 ms/40 A (buffer module with 300 ms at 40 A)
- SITOP BUF8600 4 s/40 A (buffer module with 4 s at 40 A)
- SITOP BUF8600 10 s/40 A (buffer module with 10 s at 40 A)
- SITOP UPS8600 (UPS module)
  - BAT8600 (battery module BAT8600 Pb for buffering in case of power failure 10 min/960 W)
  - BAT8600 (battery module BAT8600 LiFePO4 for buffering in case of power failure 14 min/960 W)

Up to 4 CNX8600 expansion modules and up to 2 buffer components (BUF8600 or UPS8600) can be connected to a PSU8600 basic unit. The connection is made on top of the modules without any wiring using the System Clip Link, a connecting plug for system data and power supplies. Up to six supplementary modules can be added in random order; this means that existing configurations do not have to be altered if a module is added at a later stage. Up to 5 BAT8600 battery modules of the same type can be connected to a UPS8600 module. The connection between UPS8600 and BAT8600 via the Energy Storage Link enables intelligent battery management for optimum battery life.

#### Function

#### Supply of connected loads

An individual supply voltage can be set at each output of the power supply system. This means you can supply loads with different rated voltages simultaneously with only one device. Plus the voltage drop caused by the different cable lengths can be compensated individually, which means each load can be supplied with the optimum voltage.

#### Monitoring of the outputs for overload

Each output of the power supply system is individually monitored for overload. If the load current exceeds the set response threshold, the output is shut down according to specified timecurrent characteristics. All other outputs continue to be supplied reaction-free

#### Enabling and disabling the outputs

Each output can be manually enabled or disabled directly on the device (e.g. for commissioning or service) and an overload tripping can be reset. Outputs disabled due to overload can also be reset remotely using a remote reset signal (24 V input).

In addition, program-controlled enabling and disabling of the outputs is possible using the integrated Ethernet/PROFINET interface. This also means you can disable individual outputs by means of PROFlenergy during breaks to save energy.

#### Communication

Comprehensive diagnostic information can be gueried and processed via the integrated Ethernet/PROFINET interface during operation for both the device status as well as the status of the individual outputs. This results in complete transparency, minimal downtimes and quick fault location. The integrated web server also permits remote monitoring of the power supply system.

#### Buffering

If brief voltage dips occur on the mains side, the buffer module provides the load current for supplying the outputs via its energy storage devices. Maintenance-free electrolytic capacitors or double-layer capacitors are used as energy-storage units.

UPS module UPS8600 can be used with the corresponding BAT8600 battery modules to protect against longer power failures. This allows power failures in the minutes to hours range to be bridged. These supplementary modules also make it possible to shut down the system in a specific and safe manner in the event of a power failure. For most power interruptions, however, the bridging time is sufficient so that the system can continue to run without malfunction.

SITOP PSU8600 power supply system

Introduction

#### Integration

#### Software for TIA-based automation systems

Different software components are available to facilitate easy integration of the SITOP PSU8600 in the TIA environment.

Engineering is simple via the TIA Portal. Special function blocks for SIMATIC S7-300, S7-400, S7-1200 and S7-1500 also support integration in the STEP 7 user program.

The comprehensive operating and diagnostic data of the power supply system can be visualized using ready-to-use PSU8600 faceplates for WinCC.


#### TIA Portal

- User-friendly, failsafe integration of SITOP PSU8600 in the PROFINET network by means of drag-and-drop
- Convenient configuration of the PSU8600 basic units and CNX8600 and BUF8600 add-on modules though simple selection from the TIA Portal hardware catalog from version V14 and for UPS8600 and BAT8600 as of version V15 SP1
- Free HSP (hardware support package) available for the TIA Portal at:

http://support.automation.siemens.com/WW/view/en/102254062

 Free download of GSD file (generic station description) for STEP 7 V 5.5 available from

http://support.automation.siemens.com/WW/view/en/102254061



Error-free establishment of the PROFINET connection between the SITOP PSU8600 and the controller is easy with the TIA Portal

#### STEP 7 function blocks

Function blocks are available for STEP 7 user programs on SIMATIC S7-300/400/1200/1500. They allow further processing of the PSU8600 operating data.

• Function blocks for STEP 7 V5.5

• Function blocks for STEP 7 in the TIA Portal

#### Free download at:

http://support.automation.siemens.com/WW/view/en/102379345

#### Faceplates for WinCC

Ready-to-use faceplates save programming time during visualization of the SITOP PSU8600. The faceplates show all relevant statuses and values of the power supply system and the individual outputs and are available for the following systems:

- Faceplates for WinCC from Version V7.3
- Faceplates for WinCC flexible 2008 SP3
- Faceplates for WinCC Comfort/Advanced/Professional in the TIA Portal

#### Free download at:

http://support.automation.siemens.com/WW/view/en/102379345

			SITO	P PSU8600
State	Trends	Alarms		PS
PSU8600	PSU8600 info	rmation		
CNX8600 #1 CNX8600 #2 CNX8600 #3 BUF8600 #1		ng state: 390 V voltage: 390 V current: 3.0 A	The power sup no	oply system is i rmal operatior
BUF8600 #1	Output inform	nation		
Information	Output 1: Output 2: Output 3: Output 4:	Uout:         23.9 V           Uout:         24.0 V           Uout:         24.0 V           Uout:         24.0 V	Iout: 2.6 A Iout: 0.1 A Iout: 0.1 A Iout: 0.0 A	State: State: State: State:

The pre-compiled WinCC faceplates show all the relevant data of the power supply system in an easy-to-understand display.

#### Software for SIMATIC PCS 7 process control system

The SITOP library is available with blocks and faceplates for direct integration into SIMATIC PCS 7. The SW blocks in the SIMATIC S7 supply the faceplate on the user interface of the process control system with operating and diagnostics data, generate messages and ensure connection to the maintenance system of PCS 7. This ensures constant transparency of the 24V supply in the control system. The SITOP library is supported in SIMATIC PCS 7 with SP2 as from version V8.0.

#### Free download at:

https://support.industry.siemens.com/cs/ww/en/view/109476154

#### SITOP Manager—the tool for commissioning, engineering and monitoring of communication-capable SITOP power supplies

SITOP Manager is the medium for all users who do not work with SIMATIC STEP 7 in the TIA Portal or with SIMATIC PCS 7. It manages all communication-capable power supplies in a communication network and enables their commissioning, online and offline engineering, diagnostics as well as operator control and monitoring. With the help of the SITOP Shutdown Service (autonomous function of the SITOP Manager), for example, it also supports continuous monitoring and specific shutdown of one or more PCs in case of a power failure. SITOP Manager is available as a free download in SIOS. It supports the following SITOP devices:

- Requirement for the use of SITOP Manager V1.0 with SITOP PSU8600:
- SITOP PSU8600 40 A / 4 x 10 A as of product state (PS) "2", firmware V1.4.0 and higher
- SITOP PSU8600 20 A / 4 x 5 A, 20 A, 40 A as of product state (PS) "1", firmware V1.4.0 and higher

#### Functions of the SITOP Manager

- Integrated engineering, monitoring, diagnostics and service functions save time and operating costs
- Usability via the web interface simplifies automation projects
- · Stability and quality prevent plant failures
- Shutting down specific PCs prevents data loss in the event of a power failure
- Possibility to configure multiple SITOP PSU8600 PN/USBs via a single SITOP Manager project file reduces overhead and time, thus saving costs
- The option to make configuration changes during operation (CiR) reduces plant downtimes

SITOP PSU8600 power supply system

#### Introduction

#### Integration (continued)


- Firmware update option ensures that the SITOP PSU8600 is always up-to-date
- Since SITOP Manager supports Microsoft Windows, it can be used on all common PCs
- Built-in versatility since the SITOP Manager can be operated on a wide variety of end devices, such as PCs/industrial PCs, tablets and mobiles
- Secure, encrypted communication according to the Siemens security concepts ('Security-in-depth' model)



Diagnostics via SITOP Manager

SIEMENS									SITOP Manage
Logged in ac admin Logent									e English 🖉
OFFLINE Project	(1% B	+ 014	gneetics • Object configuration	Commissioning					P508600.4 x 10A (V1.4
<ul> <li>my-poubboo</li> <li>my-shutdown-service</li> <li>my-spa1600</li> </ul>	0. 0.	Diagno Alarm I	rlics + Alarms + Alarm history Notary						4
O Add		Alar	n history						
ONLINE Connections	-	Seve	way then MAATDANCS ISOUT	40-(1) 👻 and high	er				Sent at Char Nittory
* pea PSUB600 4 x 104 (V1.4.0)		10	Event	Incoming to desired	Severity	Sheet	Bubsiet	Cate and time (UTC)	Details on event
8UF8600 100mu/404 (v1.4.0) [1]		13	Shutdown due to impormisable supply voltage	incoming	<b>13</b> >	0	•	30.06.2018 06.02.23 107	Supply votage is outside the permissible limits. Outputs of the power supply system have been switched off.
shutdown service • shutdown service			Buffer mode	incoming	21	,	•	30.08.2018 06.02.23.075	The power supply system is supplied via the buffer components.
		14	Input voltage below permitted range	Incoming	781	0	0	30.08.2018 06.02.23.05P	Input voltage bolow permitted range
Shubbourt Service (V1.8-8)					211			30.08.2018	The power supply system is supplied via the buffer components.

Alarm history in SITOP Manager



SITOP Manager UPS1600 offline, including saving of offline project to a project file

#### Free download at:

https://support.industry.siemens.com/cs/ww/en/view/109760607

#### Integration (continued)

#### Web server

A web server is integrated in the PSU8600 basic unit for remote monitoring of the power supply system.

Remote monitoring of

- Hardware configuration data
- Operating data of the basic unit, all connected add-on modules and the individual outputs
- Alarm messages

Remote access via

- Firefox V29, Internet Explorer 8, 10, 11
- IP address
- User name and password

		SITOP	PSU8
Hardware configuration		Logout	
	600 PROFINET device name: Article no.: Serial number Hardware: Pirmware:	[990           66EP3437-6M800-2CY0           O6E00UT4PWJ           1           [V1.0.0.4]	
	Operating state: Current input voltage: System load current:	The power supply system is in normal operation. 393.1 2.49	
		g data-PSU800 PSU5000 PSU5000 PROFINET davice name: Ardice no: Serial number: Istandance: Filmance: General Operating state: Current input voltage:	g stats=PRU8000  PSU8000  PSU8000  PSU8000  PROFINET divice name: Article no: GEP3137-04000-2CYT0 Gefail number: GEF0137-04000-2CYT0 GEF0137-04000-2CYT0 Gefail number: U 10.0.4  General  Correct legus value General  Correct legus value Gameral  System load current 2.24

The password-protected web server offers a view of the configuration and operating data.

#### More information

TIA Selection Tool for quick and easy configuration of the PSU8600 power supply system: http://www.siemens.com/tst

3-phase, basic units 24 V DC (PSU8600)

Overview



The 3-phase basic units of the SITOP PSU8600 power supply system include one Ethernet/PROFINET interface as well as one or four configurable outputs (voltage and current threshold) with selective monitoring. If needed, additional units from the modular system can be added to the basic unit without wiring effort in order to increase the number of outputs (CNX8600) or to extend the power buffering time (BUF8600, UPS8600). Comprehensive diagnostic and maintenance information is available via

PROFINET. It can be evaluated directly in SIMATIC S7 and visualized in SIMATIC WinCC.

Energy management is also optimally supported by collecting the energy data for each output as well as individual activation and deactivation of the outputs via PROFlenergy.

Multi-vendor transfer of parameters and diagnostic data is also possible via the open communication interface OPC UA.

#### Main product highlights

- 3-phase basic devices with one or four integrated outputs, each individually parameterizable and selectively monitored
- Extremely slim design with very high efficiency of up to 94%
- Voltage and response threshold can be set separately and are infinitely adjustable for each output
- Extra power with 1.5 times the rated current (5 s/min) for brief, operational overload
- Integrated Ethernet/PROFINET interface (2 ports)
- Easy configuration in the TIA Portal
- Open communication via integrated OPC UA server
- Integrated web server for remote diagnostics
- Comprehensive diagnostic information during operation
- Outputs can be deactivated and activated in a targeted manner with PROFlenergy
- Individual expansion options from the modular system (expansion modules (CNX8600), modules for buffering shortterm (BUF8600) or longer power failures (UPS8600 with BAT8600)) without wiring effort

#### Technical specifications

Article number	6EP3436-8SB00-2AY0	6EP3437-8SB00-2AY0	6EP3436-8MB00-2CY0	6EP3437-8MB00-2CY0
Product	SITOP PSU8600	SITOP PSU8600	SITOP PSU8600	SITOP PSU8600
Power supply, type	24 V/20 A	24 V/40 A	24 V/20 A/4x 5 A	24 V/40 A/4x 10 A
Input	21 1/20 /4			
Input	3-phase AC	3-phase AC	3-phase AC	3-phase AC
Rated voltage value $V_{\text{in rated}}$	400 500 V	400 500 V	400 500 V	400 500 V
Voltage range AC	320 575 V	320 575 V	320 575 V	320 575 V
Note	Derating 320 360 and 530 575 V	Derating 320 360 and 530 575 V	Derating 320 360 and 530 575 V	Derating 320 360 and 530 575 V
Wide-range input	Yes	Yes	Yes	Yes
Mains buffering at I <sub>out rated</sub> , min.	15 ms; at $V_{in}$ = 400 V; Prioritized voltage supply to the outputs at power failure via DIP switch can be selected (only with expansion module CNX8600)	15 ms; at $V_{\rm in}$ = 400 V; Prioritized voltage supply to the outputs at power failure via DIP switch can be selected (only with expansion module CNX8600)	15 ms; at $V_{in} =$ 400 V; Priori- tized supply Output 1 at power failure can be selected via DIP switch	15 ms; at $V_{in}$ = 400 V; Priori- tized supply Output 1 at power failure can be selected via DIP switch
Rated line frequency 1	50 Hz	50 Hz	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz	47 63 Hz	47 63 Hz
Input current				
<ul> <li>at rated input voltage 400 V</li> </ul>	1.4 A	2.75 A	1.4 A	2.75 A
<ul> <li>at rated input voltage 500 V</li> </ul>	1.1 A	2.2 A	1.1 A	2.2 A
Switch-on current limiting (+25 °C), max.	14 A	14 A	14 A	14 A
l²t, max.	1.2 A <sup>2</sup> ·s	2.24 A <sup>2</sup> ·s	1.2 A <sup>2</sup> ·s	2.24 A <sup>2</sup> ·s
Built-in incoming fuse	none	none	none	none
Protection in the mains power input (IEC 898)	Required: 3-pole connected miniature circuit breaker 6 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711- 1DD10 (UL 489)	Required: 3-pole connected miniature circuit breaker 10 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711- 1DD10 (UL 489)	Required: 3-pole connected miniature circuit breaker 6 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711- 1DD10 (UL 489)	Required: 3-pole connected miniature circuit breaker 10 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711- 1DD10 (UL 489)

Advanced power supplies SITOP PSU8600 power supply system

## 3-phase, basic units 24 V DC (PSU8600)

## Technical specifications (continued)

Article number Product	6EP3436-8SB00-2AY0 SITOP PSU8600	6EP3437-8SB00-2AY0 SITOP PSU8600	6EP3436-8MB00-2CY0 SITOP PSU8600	6EP3437-8MB00-2CY0 SITOP PSU8600
Power supply, type	24 V/20 A	24 V/40 A	24 V/20 A/4x 5 A	24 V/40 A/4x 10 A
Output				
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Number of outputs	1	1	4	4
Rated voltage Vout rated DC	24 V	24 V	24 V	24 V
<ul><li>Output voltage</li><li>at output 1 at DC Rated value</li></ul>	24 V	24 V	24 V	24 V
<ul> <li>at output 2 at DC Rated value</li> </ul>	-	-	24 V	24 V
<ul> <li>at output 3 at DC Rated value</li> </ul>	-	-	24 V	24 V
at output 4 at DC Rated value	-	-	24 V	24 V
Total tolerance, static $\pm$	3 %	3 %	3 %	3 %
Static mains compensation, approx.	0.2 %	0.2 %	0.2 %	0.2 %
Static load balancing, approx.	0.1 %	0.1 %	0.1 %	0.1 %
0.11	100 mV	100 mV	100 mV	100 mV
Residual ripple peak-peak, max.				
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV	200 mV	200 mV	200 mV
Adjustment range	4 28 V	4 28 V	4 28 V	4 28 V
Product function Output voltage adjustable	Yes	Yes	Yes	Yes
Output voltage setting	via potentiometer or IE/PN-interface; Derating > 24 V: 4%/V; max. 480 W overall system	via potentiometer or IE/PN-interface; Derating > 24 V: 4%/V; max. 960 W overall system	via potentiometer or IE/PN-interface; Derating > 24 V: 4%/V; max. 120 W per output, max. 480 W overall system	via potentiometer or IE/PN-interface; Derating > 24 V: 4%/V; max. 240 W per output, max. 960 W overall system
Status display	3-color LED for operating state device; LED for operating mode manual/ remote; 4 LEDs for communi- cation PROFINET; 3-color LED for operating state output	3-color LED for operating state device; LED for operating mode manual/ remote; 4 LEDs for communi- cation PROFINET; 3-color LED for operating state output	cation PROFINET; 3-color LED per output for operating state output; LED green for parallel operation Output 1 and 2 / 3 and 4	3-color LED for operating state device; LED for operating mode manual/ remote; 4 LEDs for communi- cation PROFINET; 3-color LED per output for operating state output; LED green for parallel operation Output 1 and 2 / 3 and 4
Signaling	Relay contact (changeover contact, contact current capacity DC 60 V/0.3 A) for "Operating state OK"	Relay contact (changeover contact, contact current capacity DC 60 V/0.3 A) for "Operating state OK"	Relay contact (changeover contact, contact current capacity DC 60 V/0.3 A) for "Operating state OK"	Relay contact (changeover contact, contact current capacity DC 60 V/0.3 A) for "Operating state OK"
On/off behavior	No overshoot of V <sub>out</sub> (soft start)	No overshoot of V <sub>out</sub> (soft start)	No overshoot of V <sub>out</sub> (soft start)	No overshoot of V <sub>out</sub> (soft start)
Startup delay, max.	1 s	1 s	1 s; Without on-delay of the outputs	1 s; Without on-delay of the outputs
connection of outputs operating	Simultaneous connecting-in of all outputs after device booting or delay time of 25 ms, 100 ms or "load- optimized" for sequential cutting-in of the outputs via DIP switches can be set (only with expansion module CNX8600)	Simultaneous connecting-in of all outputs after device booting or delay time of 25 ms, 100 ms or "load- optimized" for sequential cutting-in of the outputs via DIP switches can be set (only with expansion module CNX8600)	Simultaneous connecting-in of all outputs after device booting or delay time of 25 ms, 100 ms or "load- optimized" for sequential cutting-in of the outputs via DIP switches can be set	Simultaneous connecting-in of all outputs after device booting or delay time of 25 ms, 100 ms or "load- optimized" for sequential cutting-in of the outputs via DIP switches can be set
Voltage increase time of the output voltage maximum	500 ms	500 ms	500 ms	500 ms
Rated current value <i>I</i> <sub>out rated</sub> Output current	20 A	40 A	20 A	40 A
per output	20 A	40 A	5 A	10 A
at output 1 Rated value	20 A	40 A	5 A	10 A
at output 2 Rated value		-	5 A	10 A
at output 2 Nated value		_	5 A	10 A
at output 3 Rated value     at output 4 Rated value			5 A	10 A
		0 40 4		
Current range	0 20 A	0 40 A	0 20 A	0 40 A
Note	+50 +60 °C: Derating 2.5%/K; no derating in connection with expansion module CNX8600 and total load of the outputs at the basic device max. 240 W	+50 +60 °C: Derating 2.5%/K; no derating in connection with expansion module CNX8600 and total load of the outputs at the basic device max. 480 W	+50 +60 °C: Derating 2.5%/K; no derating in connection with expansion module CNX8600 and total load of the outputs at the basic device max. 240 W	+50 +60 °C: Derating 2.5%/K; no derating in connection with expansion module CNX8600 and total load of the outputs at the basic device max. 480 W

SITOP PSU8600 power supply system

3-phase, basic units 24 V DC (PSU8600)

Article number Product	6EP3436-8SB00-2AY0 SITOP PSU8600	6EP3437-8SB00-2AY0 SITOP PSU8600	6EP3436-8MB00-2CY0 SITOP PSU8600	6EP3437-8MB00-2CY0 SITOP PSU8600
Power supply, type	24 V/20 A	24 V/40 A	24 V/20 A/4x 5 A	24 V/40 A/4x 10 A
Output (continued)				
Supplied active power typical	480 W	960 W	480 W	960 W
Short-term overload current				
<ul> <li>at short-circuit during operation typical</li> </ul>	60 A	120 A	-	-
Note	only in operation without CNX8600 extension module	only in operation without CNX8600 extension module	-	-
Duration of overloading capability for excess current				
<ul> <li>at short-circuit during operation</li> </ul>	25 ms	25 ms	-	-
Product feature parallel switching of outputs	-	-	Yes; Parallel circuit Output 1 with 2 or Output 3 with 4 can be selected via DIP switch	Yes; Parallel circuit Output 1 with 2 or Output 3 with 4 be selected via DIP switch
Parallel switching for enhanced performance	Yes; suitable output charac- teristics via DIP switch can be selected	Yes; suitable output charac- teristics via DIP switch can be selected	No	No
Numbers of parallel switchable units for enhanced performance	2	2	-	-
Efficiency				
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	93 %	93 %	93 %	93 %
Power loss at <i>V</i> <sub>out rated</sub> , <i>I</i> <sub>out rated</sub> , approx.	34 W	72 W	34 W	72 W
Power loss [W] during no-load operation maximum	12 W	20 W	12 W	20 W
Closed-loop control				
Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	0.1 %	0.1 %	0.1 %	0.1 %
Dynamic load smoothing ( <i>I<sub>out</sub>: 50/100/50 %), U<sub>out</sub> ± typ.</i>	0.4 %	0.4 %	0.4 %	0.4 %
Setting time maximum	10 ms	10 ms	10 ms	10 ms
Protection and monitoring				
Output overvoltage protection	< 35 V	< 35 V	< 35 V	< 35 V
Property of the output Short-circuit proof	Yes	Yes	Yes	Yes
Short-circuit protection adjustable response value current of	current operation can be selected via DIP switch	Electronic overload shutdown; optional constant- current operation can be selected via DIP switch 4 40 A	electronic overload cut-off; optionally constant current operation can be selected for Output 4 via DIP switches 0.5 5 A	electronic overload cut-ol optionally constant currer operation can be selected for Output 4 via DIP switc 0.5 10 A
current-dependent overload trip type of threshold value setting	via potentiometer or	via potentiometer or	via potentiometer or	via potentiometer or
characteristics of electronic overload	IE/PN-interface $l_a > 1.0 < 1.5 \times l_a \text{ threshold}$	IE/PN-interface $l_a > 1.0 < 1.5 \times l_a \text{ threshold}$	IE/PN-interface $l_a > 1.0 < 1.5 \times l_{a \text{ threshold}}$	IE/PN-interface $l_a > 1.0 < 1.5 \times l_{a \text{ threshold}}$
switch-off	permissible for 5 s; $I_{a \text{ limit}} (= 1.5 \times I_{a \text{ threshold}})$ permissible for 200 ms	permissible for 5 s; $l_{a \text{ limit}}$ (= 1.5 x $l_{a \text{ threshold}}$ ) permissible for 200 ms	permissible for 5 s; $l_{a \text{ limit}}$ (= 1.5 x $l_{a \text{ threshold}}$ ) permissible for 200 ms	permissible for 5 s; $I_{a \text{ limit}}$ (= 1.5 x $I_{a \text{ threshold}}$ ) permi sible for 200 ms
characteristics of constant current operation	$l_{a \text{ limit}}$ (= 1.5 x $l_{a \text{ threshold}}$ ) permissible for 5 s, afterwards $l_{a \text{ threshold}}$ continuous	$J_{a \text{ limit}}$ (= 1.5 x $J_{a \text{ threshold}}$ ) permissible for 5 s, afterwards $J_{a \text{ threshold}}$ continuous	$l_{a \text{ limit}}$ (= 1.5 x $l_{a \text{ threshold}}$ ) permissible for 5 s, afterwards $l_{a \text{ threshold}}$ continuous	$l_{a \text{ limit}}$ (= 1.5 x $l_{a \text{ threshold}}$ ) permissible for 5 s, afterwards $l_{a \text{ threshold}}$ continuous
Reset	Via button or IE/PN-interface	Via button or IE/PN-interface	Via button per output or IE/PN-interface	Via button per output or IE/PN-interface
Remote reset	Non-electrically isolated 24 V input (signal level "high" at > 15 V)	Non-electrically isolated 24 V input (signal level "high" at > 15 V)	Non-electrically isolated 24 V input (signal level "high" at > 15 V)	Non-electrically isolated 2 input (signal level "high" at > 15 V)
Overcurrent overload capability in normal operation Overload/short-circuit indicator	Total system overloadable 150% <i>l<sub>a rated</sub></i> to 5 s/min 3-color LED for operating state device; 3-color LED for	Total system overloadable 150% <i>I<sub>a rated</sub></i> to 5 s/min 3-color LED for operating state device; 3-color LED for	Total system overloadable 150% <i>I<sub>a rated</sub></i> to 5 s/min 3-color LED for operating state device; 3-color LED per	Total system overloadable 150% <i>I<sub>a rated</sub></i> to 5 s/min 3-color LED for operating state device; 3-color LED
	operating state output	operating state output	output for operating state output	output for operating state output
nterface				
Specification interface Safety	Ethernet/PROFINET	Ethernet/PROFINET	Ethernet/PROFINET	Ethernet/PROFINET
Primary/secondary isolation	Yes	Yes	Yes	Yes
Galvanic isolation	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage $U_{out}$ acc. to EN 60950-1 and EN 5017

Advanced power supplies SITOP PSU8600 power supply system

## 3-phase, basic units 24 V DC (PSU8600)

## Technical specifications (continued)

Article number	6EP3436-8SB00-2AY0	6EP3437-8SB00-2AY0	6EP3436-8MB00-2CY0	6EP3437-8MB00-2CY0
Product	SITOP PSU8600	SITOP PSU8600	SITOP PSU8600	SITOP PSU8600
Power supply, type	24 V/20 A	24 V/40 A	24 V/20 A/4x 5 A	24 V/40 A/4x 10 A
Safety (continued)				
Protection class	Class I	Class I	Class I	Class I
Leakage current maximum	3.5 mA	3.5 mA	3.5 mA	3.5 mA
CE mark	Yes	Yes	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	CULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	CULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
Explosion protection	T4 Gc; cĆSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01)	IECEX EX nA nC IIC T4 Gc; ATEX (EX) II 3G EX nA nC IIC T4 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4	T4 Gc; cĆSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01
FM approval	-	-	-	-
CB approval	Yes	Yes	Yes	Yes
Marine approval	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20
EMC				
Emitted interference	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2	EN 61000-3-2	EN 61000-3-2	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data				
Ambient temperature				
<ul> <li>during operation</li> </ul>	-25 +60 °C	-25 +60 °C	-25 +60 °C	-25 +60 °C
- Note	with natural convection	with natural convection	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3; in addition 95% maximum relative humidity, but without condensation	Climate class 3K3; in addition 95% maximum relative humidity, but without condensation	Climate class 3K3; in addition 95% maximum relative humidity, but without condensation	Climate class 3K3; in addition 95% maximum relative humidity, but without condensation
Mechanics				
Connection technology	Plug-in terminals with screwed connection	Plug-in terminals with screwed connection	Plug-in terminals with screwed connection	Plug-in terminals with screwed connection
Connections				
Supply input	L1, L2, L3, PE: Plug-in terminal with 1 screwed connection each for 0.2 4 mm <sup>2</sup> single-wire / fine stranded	L1, L2, L3, PE: Plug-in terminal with 1 screwed connection each for 0.2 4 mm <sup>2</sup> single-wire / fine stranded	L1, L2, L3, PE: Plug-in terminal with 1 screwed connection each for 0.2 4 mm <sup>2</sup> single-wire / fine stranded	L1, L2, L3, PE: Plug-in terminal with 1 screwed connection each for 0.2 4 mm <sup>2</sup> single-wire / fine stranded
• Output	Output: plug-in terminals with 2 screw connectors for 0.2 4 mm <sup>2</sup> ; 0 V: screw terminal with 3 screw connectors for 0.2 4 mm <sup>2</sup>	Output: plug-in terminals with 2 screw connectors for 0.2 4 mm <sup>2</sup> ; 0 V: screw terminal with 3 screw connectors for 0.2 4 mm <sup>2</sup>	1, 2, 3, 4: Two plug-in terminals (1, 2 and 3, 4) with 2 screwed connections each for 0.2 2.5 mm <sup>2</sup> ; 0 V: Plug- in terminal with 3 screwed connections for 0.2 4 mm <sup>2</sup>	2 screwed connections each for 0.2 2.5 mm <sup>2</sup> ; 0 V: Plug in terminal with 3 screwed
Auxiliary	RST (Reset): Plug-in terminal (together with alarm signal) with 1 screwed connection for 0.2 1.5 mm <sup>2</sup>	RST (Reset): Plug-in terminal (together with alarm signal) with 1 screwed connection for 0.2 1.5 mm <sup>2</sup>	RST (Reset): Plug-in terminal (together with alarm signal) with 1 screwed connection for 0.2 1.5 mm <sup>2</sup>	RST (Reset): Plug-in termina (together with alarm signal) with 1 screwed connection for 0.2 1.5 mm <sup>2</sup>
Connections signaling contact	11, 12, 14 (alarm signal): Plug-in terminal (together with Reset) with 1 screwed connection each for 0.2 1.5 mm <sup>2</sup>	11, 12, 14 (alarm signal): Plug-in terminal (together with Reset) with 1 screwed connection each for 0.2 1.5 mm <sup>2</sup>	11, 12, 14 (alarm signal): Plug-in terminal (together with Reset) with 1 screwed connection each for 0.2 1.5 mm <sup>2</sup>	11, 12, 14 (alarm signal): Plug-in terminal (together with Reset) with 1 screwed connection each for 0.2 1.5 mm <sup>2</sup>
Product function				
removable terminal at input	Yes	Yes	Yes	Yes
removable terminal at output	Yes	Yes	Yes	Yes
Design of the interface for communi- cation	PROFINET/Ethernet: two RJ45 sockets (2-port switch)	PROFINET/Ethernet: two RJ45 sockets (2-port switch)	PROFINET/Ethernet: two RJ45 sockets (2-port switch)	PROFINET/Ethernet: two RJ45 sockets (2-port switch)
Suitability for interaction modular system	Yes	Yes	Yes	Yes
Width of the enclosure	80 mm	125 mm	100 mm	125 mm
Height of the enclosure	125 mm	125 mm	125 mm	125 mm
Depth of the enclosure	150 mm	150 mm	150 mm	150 mm

2/10

SITOP PSU8600 power supply system

3-phase, basic units 24 V DC (PSU8600)

Article number	6EP3436-8SB00-2AY0	6EP3437-8SB00-2AY0	6EP3436-8MB00-2CY0	6EP3437-8MB00-2CY0
Product	SITOP PSU8600	SITOP PSU8600	SITOP PSU8600	SITOP PSU8600
Power supply, type	24 V/20 A	24 V/40 A	24 V/20 A/4x 5 A	24 V/40 A/4x 10 A
Mechanics (continued)				
Required spacing				
• top	50 mm	50 mm	50 mm	50 mm
bottom	50 mm	50 mm	50 mm	50 mm
• left	0 mm	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm	0 mm
Weight, approx.	1.8 kg	2.6 kg	2 kg	2.6 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x15	Snaps onto DIN rail EN 60715 35x15	Snaps onto DIN rail EN 60715 35x15	Snaps onto DIN rail EN 60715 35x15
Electrical accessories	Expansion modules CNX8600, buffer modules BUF8600, UPS module UPS8600	Expansion modules CNX8600, buffer modules BUF8600, UPS module UPS8600	Expansion modules CNX8600, buffer modules BUF8600, UPS module UPS8600	Expansion modules CNX8600, buffer modules BUF8600 UPS module UPS8600
Mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification labe 20 mm × 7 mm, TI-grey 3RT2900-1SB20
MTBF at 40 °C	298 979 h	235 118 h	243 178 h	207 612 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated in voltage and ambient temperature +25 °C (unless otherwise specific

Ordering data	Article No.	Accessories (continued)	Article No.
SITOP PSU8600 3-phase, 24 V DC/20 A with PN/IE	6EP3436-8SB00-2AY0	SITOP BUF8600 100 ms buffer module	6EP4297-8HB00-0XY0
connection Stabilized power supply		For SITOP PSU8600 Buffer capacity 100 ms/40 A	
Input: 3 400 500 V AC Output: 24 V DC/20 A		SITOP BUF8600 300 ms buffer module	6EP4297-8HB10-0XY0
SITOP PSU8600 3-phase, 24 V DC/40 A with PN/IE connection	6EP3437-8SB00-2AY0	For SITOP PSU8600 Buffer capacity 300 ms/40 A	
Stabilized power supply		SITOP BUF8600 4 s buffer module	6EP4293-8HB00-0XY0
Input: 3 400 500 V ÁC Output: 24 V DC/40 A		For SITOP PSU8600 Buffer capacity 4 s/40 A	
SITOP PSU8600 3-phase, 24 V DC/20 A/4 x 5 A with PN/IE connection	6EP3436-8MB00-2CY0	SITOP BUF8600 10 s buffer module	6EP4295-8HB00-0XY0
Stabilized power supply Input: 3 400 500 V AC		For SITOP PSU8600 Buffer capacity 10 s/40 A	
Output: 24 V DC/20 A/4 x 5 A		SITOP UPS8600 UPS module	6EP4197-8AB00-0XY0
SITOP PSU8600 3-phase, 24 V DC/40 A/4 x 10 A with PN/IE	6EP3437-8MB00-2CY0	For SITOP PSU8600 Rated buffer power 960 W	
connection Stabilized power supply		SITOP BAT8600 battery module 380 Wh	6EP4145-8GB00-0XY0
Input: 3 400 500 V AC Output: 24 V DC/40 A/4 x 10 A		For SITOP UPS8600 With lead batteries (Pb technology)	
		SITOP BAT8600 battery module	6EP4143-8JB00-0XY0
Accessories	Article No.		
SITOP CNX8600 4 x 5 A	6EP4436-8XB00-0CY0	For SITOP UPS8600 With lithium iron phosphate	
expansion module	0L1 ++30-0AB00-0010	batteries (LiFePO4 technology)	
For SITOP PSU8600 Output: 24 V DC/4 x 5 A		Device identification label	3RT2900-1SB20
SITOP CNX8600 4 x 10 A expansion module	6EP4437-8XB00-0CY0		

For SITOP PSU8600 Output: 24 V DC/4 x 10 A SITOP CNX8600 8 x 2.5 A expansion module

For SITOP PSU8600 Output: 24 V DC/8 x 2.5 A

6EP4436-8XB00-0DY0

SITOP PSU8600 power supply system

#### Modular system, expansion of outputs (CNX8600)

#### Overview



The CNX8600 expansion modules are part of the SITOP PSU8600 modular system and expand the basic unit by increasing the number of selectively monitored outputs.

You can connect up to four CNX8600 expansion modules to the PSU8600 basic device. The connection is made on top of the modules without any wiring using the System Clip Link, a connecting plug for system data and power supplies.

#### Main product highlights

- · Available modules:
  - Four integrated outputs with up to 5 A each and selective monitoring
  - Four integrated outputs with up to 10 A each and selective monitoring
  - Eight integrated outputs with up to 2.5 A each and selective monitoring
- Voltage and response threshold can be set separately and are infinitely adjustable for each output
- Comprehensive diagnostic information during operation via the PSU8600 basic unit
- Outputs can be activated and deactivated in a targeted manner with PROFlenergy via the PSU8600 basic unit

User-friendly connection without the need for wiring thanks to System Clip Link.

#### Technical specifications

Article number	6EP4436-8XB00-0CY0	6EP4437-8XB00-0CY0	6EP4436-8XB00-0DY0
Product	SITOP CNX8600	SITOP CNX8600	SITOP CNX8600
Power supply, type	4x 5 A	4x 10 A	8x 2.5 A
Output			
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Number of outputs	4	4	8
Rated voltage Vout rated DC	24 V	24 V	24 V
Output voltage			
<ul> <li>at output 1 at DC Rated value</li> </ul>	24 V	24 V	24 V
<ul> <li>at output 2 at DC Rated value</li> </ul>	24 V	24 V	24 V
<ul> <li>at output 3 at DC Rated value</li> </ul>	24 V	24 V	24 V
<ul> <li>at output 4 at DC Rated value</li> </ul>	24 V	24 V	24 V
<ul> <li>at output 5 at DC Rated value</li> </ul>	-	-	24 V
<ul> <li>at output 6 at DC Rated value</li> </ul>	-	-	24 V
<ul> <li>at output 7 at DC Rated value</li> </ul>	-	-	24 V
<ul> <li>at output 8 at DC Rated value</li> </ul>	-	-	24 V
Total tolerance, static $\pm$	3 %	3 %	3 %
Static mains compensation, approx.	0.2 %	0.2 %	0.2 %
Static load balancing, approx.	0.1 %	0.1 %	0.1 %
Residual ripple peak-peak, max.	100 mV	100 mV	100 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV	200 mV	200 mV
Adjustment range	4 28 V	4 28 V	4 28 V
Product function Output voltage adjustable	Yes	Yes	Yes
Output voltage setting	via potentiometer or IE/PN-interface; Derating > 24 V: 4%/V; max. 120 W per output	via potentiometer or IE/PN-interface; Derating > 24 V: 4%/V; max. 240 W per output	via potentiometer or IE/PN-interface; Derating > 24 V: 4%/V; max. 60 W per output
Status display	3-color LED for operating state module; 3-color LED per output for operating state output	3-color LED for operating state module; 3-color LED per output for operating state output	3-color LED for operating state module; 3-color LED per output for operating state output

## Modular system, expansion of outputs (CNX8600)

Article number	6EP4436-8XB00-0CY0	6EP4437-8XB00-0CY0	6EP4436-8XB00-0DY0
Product	SITOP CNX8600	SITOP CNX8600	SITOP CNX8600
Power supply, type	4x 5 A	4x 10 A	8x 2.5 A
Dutput (continued)			
Signaling	Relay contact (changeover contact, contact current capacity DC 60 V/0.3 A) for "Operating state OK" at power supply unit PSU8600	Relay contact (changeover contact, contact current capacity DC 60 V/0.3 A) for "Operating state OK" at power supply unit PSU8600	Relay contact (changeover contact contact current capacity DC 60 V/0.3 A) for "Operating state OK" at power supply unit PSU8600
On/off behavior	No overshoot of Vout (soft start)	No overshoot of Vout (soft start)	No overshoot of Vout (soft start)
Startup delay, max.	1.5 s; Without on-delay of the outputs	1.5 s; Without on-delay of the outputs	1.5 s; Without on-delay of the output
connection of outputs operating	Simultaneous connecting-in of all outputs after device booting or delay time of 25 ms, 100 ms or "load- optimized" for sequential cutting-in of the outputs via DIP switches at power supply unit PSU8600 can be set	Simultaneous connecting-in of all outputs after device booting or delay time of 25 ms, 100 ms or "load- optimized" for sequential cutting-in of the outputs via DIP switches at power supply unit PSU8600 can be set	Simultaneous connecting-in of all outputs after device booting or del time of 25 ms, 100 ms or "load- optimized" for sequential cutting-in the outputs via DIP switches at por supply unit PSU8600 can be set
Voltage increase time of the output voltage maximum	500 ms	500 ms	500 ms
Rated current value I <sub>out rated</sub>	20 A	40 A	20 A
Output current			
<ul> <li>per output</li> </ul>	5 A	10 A	2.5 A
<ul> <li>at output 1 Rated value</li> </ul>	5 A	10 A	2.5 A
<ul> <li>at output 2 Rated value</li> </ul>	5 A	10 A	2.5 A
<ul> <li>at output 3 Rated value</li> </ul>	5 A	10 A	2.5 A
<ul> <li>at output 4 Rated value</li> </ul>	5 A	10 A	2.5 A
<ul> <li>at output 5 Rated value</li> </ul>	-	-	2.5 A
<ul> <li>at output 6 Rated value</li> </ul>	-	-	2.5 A
<ul> <li>at output 7 Rated value</li> </ul>	-	-	2.5 A
<ul> <li>at output 8 Rated value</li> </ul>	-	-	2.5 A
Current range	0 20 A	0 40 A	0 20 A
• Note	No increase in the maximum output power of the overall system SITOP PSU8600 via the expansion module SITOP CNX8600 possible	No increase in the maximum output power of the overall system SITOP PSU8600 via the expansion module SITOP CNX8600 possible	Outputs meet requirements to NEC Class 2; an increase of the maximu output power of the SITOP PSU860 overall system is not possible over SITOP CNX8600 expansion modul
Supplied active power typical	480 W	960 W	480 W
Product feature parallel switching of outputs	No	No	No
Parallel switching for enhanced performance	No	No	No
Efficiency			
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	97 %	97 %	97 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	15 W	30 W	15 W
Closed-loop control			
Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	0.1 %	0.1 %	0.1 %
Dynamic load smoothing ( <i>l<sub>out</sub>: 50/100/50 %), U<sub>out</sub> ± typ.</i>	0.4 %	0.4 %	0.4 %
Setting time maximum	10 ms	10 ms	10 ms
Protection and monitoring			
Output overvoltage protection Property of the output Short-circuit proof	< 35 V Yes	< 35 V Yes	< 35 V Yes
Short-circuit protection adjustable response value current of	electronic overload cut-off	electronic overload cut-off 0.5 10 A	electronic overload cut-off 0.5 2.5 A

2

SITOP PSU8600 power supply system

## Modular system, expansion of outputs (CNX8600)

## Technical specifications (continued)

Article number	6EP4436-8XB00-0CY0	6EP4437-8XB00-0CY0	6EP4436-8XB00-0DY0
Product	SITOP CNX8600	SITOP CNX8600	SITOP CNX8600
Power supply, type	4x 5 A	4x 10 A	8x 2.5 A
Protection and monitoring (continued)			
type of threshold value setting	via potentiometer or IE/PN-interface	via potentiometer or IE/PN-interface	via potentiometer or IE/PN-interface
characteristics of electronic overload switch-off	$l_a > 1.0 < 1.5 \times l_a \text{ threshold permissible}$ for 5 s; $l_a \text{ limit} (= 1.5 \times l_a \text{ threshold})$ permissible for 200 ms	$l_a > 1.0 < 1.5 \times l_a$ threshold permissible for 5 s; $l_a$ limit (= 1.5 × $l_a$ threshold) permissible for 200 ms	$I_a > 1.0 < 1.5 \times I_a \text{ threshold permissible}$ for 5 s; $I_a \text{ limit} (= 1.5 \times I_a \text{ threshold})$ permissible for 200 ms
Reset	Via button per output or IE/PN-interface	Via button per output or IE/PN-interface	Via button per output or IE/PN-interface
Remote reset	Non-electrically isolated 24 V input (signal level "high" at > 15 V) at power supply unit PSU8600	Non-electrically isolated 24 V input (signal level "high" at > 15 V) at power supply unit PSU8600	Non-electrically isolated 24 V input (signal level "high" at > 15 V) at power supply unit PSU8600
Overload/short-circuit indicator	3-color LED for operating state module; 3-color LED per output for operating state output	3-color LED for operating state module; 3-color LED per output for operating state output	3-color LED for operating state module; 3-color LED per output for operating state output
Interface			
Specification interface	Ethernet/PROFINET via power supply unit PSU8600	Ethernet/PROFINET via power supply unit PSU8600	Ethernet/PROFINET via power supply unit PSU8600
Safety			
Primary/secondary isolation	Yes	Yes	Yes
Galvanic isolation	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178
Protection class	Class III	Class III	Class III
CE mark	Yes	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1), NEC class 2
Explosion protection		IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4	
CB approval	Yes	Yes	Yes
Marine approval	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL
Degree of protection (EN 60529)	IP20	IP20	IP20
EMC			
Emitted interference	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data			
Ambient temperature			
<ul> <li>during operation</li> </ul>	-25 +60 °C	-25 +60 °C	-25 +60 °C
- Note	with natural convection	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C
during storage	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3; in addition 95% maximum relative humidity, but without condensation	Climate class 3K3; in addition 95% maximum relative humidity, but without condensation	Climate class 3K3; in addition 95% maximum relative humidity, but without condensation

## Modular system, expansion of outputs (CNX8600)

Product Power supply, type Mechanics Connection technology Connections • Output Product function • removable terminal at output Suitability for interaction modular system Type of connection to system compo-	SITOP CNX8600 4x 5 A Plug-in terminals with screwed connection 1, 2, 3, 4: Two plug-in terminals (1, 2 and 3, 4) with 2 screwed connections each for 0.2 2.5 mm <sup>2</sup> ; Ground: Plug-in terminal with 3 screwed connections for 0.2 2.5 mm <sup>2</sup> Yes Yes Via integrated connector 60 mm	SITOP CNX8600 4x 10 A Plug-in terminals with screwed connection 1, 2, 3, 4: Two plug-in terminals (1, 2 and 3, 4) with 2 screwed connections each for 0.2 2.5 mm <sup>2</sup> ; Ground: Plug-in terminal with 3 screwed connections for 0.2 2.5 mm <sup>2</sup> Yes Yes Via integrated connector	SITOP CNX8600 8x 2.5 A Plug-in terminals with screwed connection 1, 2, 3, 4, 5, 6, 7, 8: Two plug-in terminals (14 and 58) with 1 screwed connection each for 0.2 2.5 mm <sup>2</sup> ; Ground: Plug-in terminal with 3 screwed connection for 0.2 2.5 mm <sup>2</sup> Yes Yes Via integrated connector
Mechanics Connection technology Connections • Output Product function • removable terminal at output Suitability for interaction modular system Type of connection to system compo-	Plug-in terminals with screwed connection 1, 2, 3, 4: Two plug-in terminals (1, 2 and 3, 4) with 2 screwed connections each for 0.2 2.5 mm <sup>2</sup> ; Ground: Plug-in terminal with 3 screwed connections for 0.2 2.5 mm <sup>2</sup> Yes Yes	Plug-in terminals with screwed connection 1, 2, 3, 4: Two plug-in terminals (1, 2 and 3, 4) with 2 screwed connections each for 0.2 2.5 mm <sup>2</sup> ; Ground: Plug-in terminal with 3 screwed connections for 0.2 2.5 mm <sup>2</sup> Yes	Plug-in terminals with screwed connection 1, 2, 3, 4, 5, 6, 7, 8: Two plug-in terminals (14 and 58) with 1 screwed connection each for 0.2 2.5 mm <sup>2</sup> ; Ground: Plug-in terminal with 3 screwed connection for 0.2 2.5 mm <sup>2</sup> Yes Yes
Connection technology Connections • Output Product function • removable terminal at output Suitability for interaction modular system Type of connection to system compo-	<ul> <li>connection</li> <li>1, 2, 3, 4: Two plug-in terminals <ul> <li>(1, 2 and 3, 4) with 2 screwed</li> <li>connections each for 0.2 2.5 mm<sup>2</sup>;</li> <li>Ground: Plug-in terminal with 3 screwed connections for</li> <li>0.2 2.5 mm<sup>2</sup></li> </ul> </li> <li>Yes <ul> <li>Yes</li> <li>Yes</li> <li>Via integrated connector</li> </ul> </li> </ul>	connection 1, 2, 3, 4: Two plug-in terminals (1, 2 and 3, 4) with 2 screwed connections each for 0.2 2.5 mm <sup>2</sup> ; Ground: Plug-in terminal with 3 screwed connections for 0.2 2.5 mm <sup>2</sup> Yes Yes	connection 1, 2, 3, 4, 5, 6, 7, 8: Two plug-in terminals (14 and 58) with 1 screwed connection each for 0.22.5 mm <sup>2</sup> ; Ground: Plug-in terminal with 3 screwed connection for 0.22.5 mm <sup>2</sup> Yes Yes
Connections • Output Product function • removable terminal at output Suitability for interaction modular system Type of connection to system compo-	<ul> <li>connection</li> <li>1, 2, 3, 4: Two plug-in terminals <ul> <li>(1, 2 and 3, 4) with 2 screwed</li> <li>connections each for 0.2 2.5 mm<sup>2</sup>;</li> <li>Ground: Plug-in terminal with 3 screwed connections for</li> <li>0.2 2.5 mm<sup>2</sup></li> </ul> </li> <li>Yes <ul> <li>Yes</li> <li>Yes</li> <li>Via integrated connector</li> </ul> </li> </ul>	connection 1, 2, 3, 4: Two plug-in terminals (1, 2 and 3, 4) with 2 screwed connections each for 0.2 2.5 mm <sup>2</sup> ; Ground: Plug-in terminal with 3 screwed connections for 0.2 2.5 mm <sup>2</sup> Yes Yes	connection 1, 2, 3, 4, 5, 6, 7, 8: Two plug-in terminals (14 and 58) with 1 screwed connection each for 0.22.5 mm <sup>2</sup> ; Ground: Plug-in terminal with 3 screwed connection for 0.22.5 mm <sup>2</sup> Yes Yes
<ul> <li>Output</li> <li>Product function</li> <li>removable terminal at output</li> <li>Suitability for interaction modular system</li> <li>Type of connection to system compo-</li> </ul>	<ul> <li>(1, 2 and 3, 4) with 2 screwed connections each for 0.2 2.5 mm<sup>2</sup>; Ground: Plug-in terminal with 3 screwed connections for 0.2 2.5 mm<sup>2</sup></li> <li>Yes Yes</li> <li>Via integrated connector</li> </ul>	(1, 2 and 3, 4) with 2 screwed connections each for 0.2 2.5 mm <sup>2</sup> ; Ground: Plug-in terminal with 3 screwed connections for 0.2 2.5 mm <sup>2</sup> Yes Yes	terminals (14 and 58) with 1 screwed connection each for 0.2 2.5 mm <sup>2</sup> ; Ground: Plug-in terminal with 3 screwed connection for 0.2 2.5 mm <sup>2</sup> Yes Yes
Product function • removable terminal at output Suitability for interaction modular system Type of connection to system compo-	<ul> <li>(1, 2 and 3, 4) with 2 screwed connections each for 0.2 2.5 mm<sup>2</sup>; Ground: Plug-in terminal with 3 screwed connections for 0.2 2.5 mm<sup>2</sup></li> <li>Yes Yes</li> <li>Via integrated connector</li> </ul>	(1, 2 and 3, 4) with 2 screwed connections each for 0.2 2.5 mm <sup>2</sup> ; Ground: Plug-in terminal with 3 screwed connections for 0.2 2.5 mm <sup>2</sup> Yes Yes	terminals (14 and 58) with 1 screwed connection each for 0.2 2.5 mm <sup>2</sup> ; Ground: Plug-in terminal with 3 screwed connection for 0.2 2.5 mm <sup>2</sup> Yes Yes
removable terminal at output Suitability for interaction modular system Type of connection to system compo-	Yes - Via integrated connector	Yes	Yes
Suitability for interaction modular system Type of connection to system compo-	Yes - Via integrated connector	Yes	Yes
system Type of connection to system compo-	- Via integrated connector		
	J. J	Via integrated connector	Via integrated connector
nents	60 mm		
Width of the enclosure		60 mm	100 mm
Height of the enclosure	125 mm	125 mm	125 mm
Depth of the enclosure	150 mm	150 mm	150 mm
Required spacing			
• top	50 mm	50 mm	50 mm
bottom	50 mm	50 mm	50 mm
• left	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm
Weight, approx.	1.15 kg	1.15 kg	1.29 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x15	Snaps onto DIN rail EN 60715 35x15	Snaps onto DIN rail EN 60715 35x
Mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20
MTBF at 40 °C	358 372 h	358 372 h	327 369 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltag and ambient temperature +25 °C (unless otherwise specified)
Ordering data	Article No.	Accessories	Article No.
SITOP CNX8600 4 x 5 A expansion module	6EP4436-8XB00-0CY0	Device labeling plates	3RT2900-1SB20
For SITOP PSU8600 Output: 24 V DC/4 x 5 A			
SITOP CNX8600 4 x 10 A expansion module	6EP4437-8XB00-0CY0		

## Technical specifications (continued)

For SITOP PSU8600 Output: 24 V DC/4 x 10 A

SITOP CNX8600 8 x 2.5 A expansion module

For SITOP PSU8600 Output: 24 V DC/8 x 2.5 A 6EP4436-8XB00-0DY0

2

SITOP PSU8600 power supply system

#### Modular system, buffering (BUF8600 and UPS8600)

#### Overview



SITOP BUF8600 for buffering brief power interruptions

The BUF8600 buffer modules with maintenance free energy storage units are part of the SITOP PSU8600 modular system and are designed to bridge short-term power failures. They automatically take over the DC power supply in case of a line voltage failure. You can connect up to two BUF8600 buffer modules to the PSU8600 basic unit. The connection is made on top of the modules without any wiring using the System Clip Link, a connecting plug for system data and power supplies. Main product highlights

- Reliable bridging of short-term power failures up to max. 20 s for an output power of 960 W
- Buffer module with maintenance free electrolytic capacitors for bridging short-term power failures (brownouts) between 100 ms and max. 600 ms (at 24 V DC/40 A)
- Buffer module with maintenance free double-layer capacitors for bridging longer power failures between 4 s and max. 20 s (at 24 V DC/40 A)
- The two buffer modules can be combined as required
- · Easy connection without wiring overhead

#### SITOP UPS8600 for buffering longer power failures

UPS module UPS8600 is part of the modular system of the SITOP PSU8600 and is used to bridge power failures in the range of minutes to hours. It can be supplemented with a maximum of five SITOP BAT8600 battery modules of the same design as the external energy storage. The battery modules in lithium iron phosphate (LiFePO4) technology have a typical buffer time of 14 minutes at full load (960 W). The lead-acid batteries (Pb) offer a typical power consumption at full load (960 W). Buffer time of 10 minutes.

#### Main product highlights

- Power failure bridging in the hours range facilitate continuous system operation
- Prioritized output buffering of the PSU8600 power supply system possible
- Automatic recognition of BAT8600 "Pb" and BAT8600
   "LiFePO4" battery modules
- Intelligent battery managementfor optimum charging and monitoring via the Energy Storage Link
- Complete system integration in TIA or OPC UA environment for engineering and diagnostic functions
- Selective shutdown of IPCsvia Ethernet interface (PROFINET/OPC UA protocol)
- User-friendly connection system without wiring work thanks to System Clip Link (UPS8600)

#### Technical specifications

Article number	6EP4297-8HB00-0XY0	6EP4297-8HB10-0XY0	6EP4293-8HB00-0XY0	6EP4295-8HB00-0XY0
Product brand name	SITOP BUF8600	SITOP BUF8600	SITOP BUF8600	SITOP BUF8600
Type of current supply	100 ms/40 A	300 ms/40 A	4 s/40 A	10 s/40 A
Mains buffering				
Type of energy storage	electrolytic capacitors	electrolytic capacitors	Double-layer capacitors	Double-layer capacitors
Design of the mains power cut bridging-connection	Backup time with 40 A load current: 100 ms	Backup time with 40 A load current: 300 ms	Backup time with 40 A load current: 4 s	Backup time with 40 A load current: 10 s
Buffering time for rated value of the output current in the event of power failure	100 ms	300 ms	4 000 ms	10 000 ms
Output				
Output current				
Rated value	40 A	40 A	40 A	40 A
Signaling				
Display version	3-color LED for operating state module			
<ul> <li>for normal operation</li> </ul>	LED green for "buffer standby exist"			
<ul> <li>in buffering mode</li> </ul>	LED yellow for "buffered mode"			
Interface				
Design of the interface	Ethernet/PROFINET via power supply unit PSU8600			

## Advanced power supplies SITOP PSU8600 power supply system

Modular system, buffering (BUF8600 and UPS8600)

Article number Product brand name Type of current supply	6EP4297-8HB00-0XY0 SITOP BUF8600 100 ms/40 A	6EP4297-8HB10-0XY0 SITOP BUF8600 300 ms/40 A	6EP4293-8HB00-0XY0 SITOP BUF8600 4 s/40 A	6EP4295-8HB00-0XY0 SITOP BUF8600 10 s/40 A
Safety				
Operating resource protection class Certificate of suitability	Class III	Class III	Class III	Class III
CE marking	Yes	Yes	Yes	Yes
• as approval for USA	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	CULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	CULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1 UL 60950-1)
<ul> <li>relating to ATEX</li> </ul>	IECEx nA IIC T5 Gc; ATEX (EX) II 3G Ex nA IIC T5 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T5	IECEx nA IIC T5 Gc; ATEX (EX) II 3G Ex nA IIC T5 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T5	IECEx nA IIC T5 Gc; ATEX (EX) II 3G Ex nA IIC T5 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T5	IECEx nA IIC T5 Gc; ATE (EX) II 3G Ex nA IIC T5 G cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group AB0 T5
Type of certification CB-certificate	Yes	Yes	Yes	Yes
Shipbuilding approval	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL
Protection class IP	IP20	IP20	IP20	IP20
	11 20	11 20		
Standard				
<ul> <li>for emitted interference</li> </ul>	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
<ul> <li>for interference immunity</li> </ul>	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data				
Ambient temperature				
during operation	-25 +60 °C; with natural convection	-25 +60 °C; with natural convection	-25 +60 °C; with natural convection	-25 +60 °C; with nature convection
<ul> <li>during transport</li> </ul>	-40 +70 °C	-40 +70 °C	-40 +70 °C	-40 +70 °C
<ul> <li>during storage</li> </ul>	-40 +70 °C	-40 +70 °C	-40 +70 °C	-40 +70 °C
Environmental category acc. to IEC 60721	Climate class 3K3; in addition 95% maximum relative humidity, but without	Climate class 3K3; in addition 95% maximum relative humidity, but without	Climate class 3K3; in addition 95% maximum relative humidity, but without	Climate class 3K3; in addition 95% maximur relative humidity, but with
Mashaulas	condensation	condensation	condensation	condensation
Mechanics				
Type of electrical connection	-	-	Plug-in terminal with screw connectors	Plug-in terminal with scree connectors
at input	-	-	-	-
<ul> <li>at output</li> </ul>	-	-	-	-
<ul> <li>for control circuit and status message</li> </ul>	-	-	X1, X2 (control contact) and 13,14, 23, 24 (message signals): 1 screw terminal each for 0.2 1.5 mm <sup>2</sup>	X1, X2 (control contact) a 13,14, 23, 24 (message signals): 1 screw termina each for 0.2 1.5 mm <sup>2</sup>
Type of connection to system compo- nents	Via integrated connector	Via integrated connector	Via integrated connector	Via integrated connector
Width of the enclosure	60 mm	125 mm	60 mm	125 mm
Height of the enclosure	125 mm	125 mm	125 mm	125 mm
Depth of the enclosure	150 mm	150 mm	150 mm	150 mm
Required spacing				
• top	50 mm	50 mm	50 mm	50 mm
• bottom	50 mm	50 mm	50 mm	50 mm
• left	0 mm	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm	0 mm
•	1.33 kg			
Net weight Product feature of the enclosure housing for side-by-side mounting	Yes	2.26 kg Yes	1.25 kg Yes	1.95 kg Yes
Mounting type	Snaps onto DIN rail EN 60715 35x15	Snaps onto DIN rail EN 60715 35x15	Snaps onto DIN rail EN 60715 35x15	Snaps onto DIN rail EN 60715 35x15
Mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification label 20 mm × 7 mm, Tl-grey 3RT2900-1SB20	Device identification labe 20 mm × 7 mm, TI-grey 3RT2900-1SB20
MTBF at 40 °C	4 505 531 h	4 505 531 h	1 374 707 h	1 190 747 h
Reference code acc. to DIN EN 81346-2	Т	Т	Т	Т
Other information	voltage and ambient temperature +25 °C	voltage and ambient temperature +25 °C	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	voltage and ambient temperature +25 °C

Advanced power supplies SITOP PSU8600 power supply system

## Modular system, buffering (BUF8600 and UPS8600)

## Technical specifications (continued)

recimical specifications (conti	naca)
Article number	6EP4197-8AB00-0XY0
Product brand name	SITOP UPS8600
Type of current supply	960 W
Mains buffering	
Type of energy storage	External battery module
Design of the mains power cut bridging-connection	Buffer time limit 1 88 min. can be set with DIP switches or until the connected battery modules are discharged
Charging current	1.25 A - 2.5 A
adjustable charging current maximum Note	Charging capacity 60 W/120 W, can be set with DIP switches
Output	
Output voltage	
<ul> <li>in normal operation at DC Rated value</li> </ul>	48 V
Property of the output Short-circuit proof	Yes
Efficiency	
Efficiency in percent	
<ul> <li>in case of accumulator operation typical</li> </ul>	99 %
Power loss [W]	
<ul> <li>in case of accumulator operation typical</li> </ul>	10 W
Protection and monitoring	
Product function	
reverse polarity protection against energy storage unit polarity reversal	Yes
Signaling	
Display version	Three-color LED for operating state of module, three-color LED for status of battery circuit
<ul> <li>for normal operation</li> </ul>	LED green for "buffer standby exist"
<ul> <li>in buffering mode</li> </ul>	LED yellow for "buffered mode"
Interface	
Design of the interface	Ethernet/PROFINET via power supply unit PSU8600
Safety	
Operating resource protection class	Class III
Certificate of suitability	
CE marking	Yes
• as approval for USA	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950- 1)
<ul> <li>relating to ATEX</li> </ul>	LECEX EX NA NC IIC T4 GC; ATEX (EX) II 3G EX NA NC IIC T4 GC; cCSAus (CSA C22.2 No. 213, ANSI/ ISA-12.12.01) Class I, Div. 2, Group ABCD, T4
Type of certification CB-certificate	Yes
Shipbuilding approval	DNV GL; ABS in process
Protection class IP	IP20

Article number	6EP4197-8AB00-0XY0
Product brand name	SITOP UPS8600
Type of current supply	960 W
EMC	
Standard	
<ul> <li>for emitted interference</li> </ul>	EN 55022 Class B
<ul> <li>for interference immunity</li> </ul>	EN 61000-6-2
Operating data	
Ambient temperature	
<ul> <li>during operation</li> </ul>	-25 +70 °C; with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C
Environmental category acc. to IEC 60721	Climate class 3K3; in addition 95% maximum relative humidity, but without condensation
Mechanics	
Type of electrical connection	Plug-in terminals with screwed connection
for battery module	+, -: Plug-in terminal with 1 screwed connection each for 0.2 10 mm <sup>2</sup>
Type of connection to system components	Via integrated connector
Width of the enclosure	60 mm
Height of the enclosure	125 mm
Depth of the enclosure	150 mm
Required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
Net weight	0.9 kg
Product feature of the enclosure housing for side-by-side mounting	Yes
Mounting type	Snaps onto DIN rail EN 60715 35x15
Electrical accessories	Battery module BAT8600
Mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20
MTBF at 40 °C	405 763 h
Reference code acc. to DIN EN 81346-2	Т
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

SITOP PSU8600 power supply system

Modular system, buffering (BUF8600 and UPS8600)

Article number	6EP4145-8GB00-0XY0	6EP4143-8JB00-0XY0
Product	SITOP BAT8600 Pb	SITOP BAT8600 LiFePO4
Product type	Battery module 380 Wh	Battery module 264 Wh
Output	Dattery module 500 with	Dattery module 204 with
Rated voltage V <sub>out rated</sub> DC	48 V	48 V
Rated current value <i>I</i> <sub>out rated</sub>		
	20 A	20 A
Safety Short-circuit protection	Plada tupa fuga 40 A FR V DC	Plade type fues 40 A F8 V DC
'	Blade-type fuse 40 A, 58 V DC	Blade-type fuse 40 A, 58 V DC
Design of the overload protection	Valve control	Valve control
Safety	Class III	
Protection class	Class III	Class III
Degree of protection (EN 60529)	IP20	IP20
Approvals		
CE mark	Yes	Yes
UL/cUL (CSA) approval	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
Explosion protection	IECEx Ex nA IIC T5 Gc; ATEX (EX) II 3G Ex nA IIC T5 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T5	
Marine approval	DNV GL; ABS in process	DNV GL; ABS in process
Environmental conditions	· · ·	
Operating data note	For storage, mounting and operation of batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/EN 50272-2) must be observed.	For storage, mounting and operation of batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/EN 50272-2) must be observed.
Ambient temperature		
<ul> <li>during operation</li> </ul>	-10 +50 °C	-10 +50 °C
during transport	-40 +60 °C	-40 +80 °C
during storage	-15 +40 °C	-40 +35 °C
Service life		
Service life of energy storage		
typical Note	capacity falls to 80 % of original capacity (according to EUROBAT)	capacity falls to 80 % of original capacity (according to EUROBAT)
<ul> <li>at 20 °C typical</li> </ul>	4 y	15 y
• at 30 °C typical	2 y	10 y
• at 40 °C typical	1 y	9 y
• at 50 °C typical	0.5 y	2 y
Ambient temperature during storage Note	In addition to the storage temperature, additional factors, such as storage duration and charging status during storage, have a major impact on the potential service life. This means batteries should preferably be stored fully charged for short periods of time in a dry, cool and frost-proof (temperature range 0 to +20 °C) location.	In addition to the storage temperature, additional factor such as storage duration and charging status during storage, have a major impact on the potential service li This means batteries should preferably be stored fully charged for short periods of time in a dry, cool and fros proof (temperature range 0 to +20 °C) location.
Mechanics		
Connection technology	Plug-in terminals with screwed connection	Plug-in terminals with screwed connection
Connection for power supply unit	+, -: 2 plug-in terminals with 1 screwed connection each for 0.2 $\dots$ 10 $\text{mm}^2$	+, -: 2 plug-in terminals with 1 screwed connection each 0.2 10 $\mbox{mm}^2$
Product component belonging to	2x blade-type fuse 40 A, 58 V DC	2x blade-type fuse 40 A, 58 V DC
Width of the enclosure	322 mm	322 mm
Height of the enclosure	187 mm	187 mm
Depth of the enclosure	110 mm	110 mm
Installation width	322 mm	322 mm
Installation height	207 mm	207 mm
Weight, approx.	13 kg	6.5 kg
Installation	Keyhole mounting for hooking in to M4 screws	Keyhole mounting for hooking in to M4 screws
Reference code acc. to DIN EN 81346-2	G	G
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Advanced power supplies SITOP PSU8600 power supply system

Modular system,	buffering (BUF8600	and UPS8600)
-----------------	--------------------	--------------

Ordering data	Article No.	Ordering data (continued)	Article No.
SITOP BUF8600 100 ms buffer module	6EP4297-8HB00-0XY0	SITOP BAT8600 battery module 380 Wh	6EP4145-8GB00-0XY0
For SITOP PSU8600 Buffer capacity 100 ms/40 A		For SITOP UPS8600 With lead batteries (Pb technology)	
SITOP BUF8600 300 ms buffer module	6EP4297-8HB10-0XY0	SITOP BAT8600 battery module 264 Wh	6EP4143-8JB00-0XY0
For SITOP PSU8600 Buffer capacity 300 ms/40 A		For SITOP UPS8600 With lithium iron phosphate	
SITOP BUF8600 4 s buffer module	6EP4293-8HB00-0XY0	batteries (LiFePO4 technology)	
For SITOP PSU8600 Buffer capacity 4 s/40 A		Accessories	Article No.
SITOP BUF8600 10 s buffer module	6EP4295-8HB00-0XY0	Device labeling plates	3RT2900-1SB20
For SITOP PSU8600 Buffer capacity 10 s/40 A			
SITOP UPS8600 UPS module	6EP4197-8AB00-0XY0		
For SITOP PSU8600 Rated buffer power 960 W			

### Overview

#### More information

Select the appropriate power supply quickly and easily with the TIA Selection Tool: http://www.siemens.com/tst



#### The technology power supply for demanding solutions

The single-phase, two-phase and three-phase SITOP modular units are the technology power supplies for demanding solutions. They offer maximum functionality for use in complex plants and machines. The wide-range input allows a connection to almost any electrical power system worldwide and ensures a high degree of safety even if there are large voltage fluctuations. They offer outstanding overload characteristics: Power boost delivers up to three-times the rated current for short periods of time, and with extra power of 150%, loads with high power consumption can be connected without any problems. And in the event of an overload, you can choose between constant current or automatic restart. The extremely high efficiency keeps energy consumption and heat buildup in the control cabinet low, and the compact metal enclosure also saves space.

To further increase the 24 V availability, the SITOP smart power supplies can be combined with **buffer**, **DC UPS**, **redundancy** and **selectivity modules**.

#### Main product highlights

- 1-phase, 24 V DC / 5 A, 10 A, 20 A, 40 A
- 1-phase and 2-phase, 24 V DC / 5A, 10 A
- 3-phase, 24 V DC/ 20 A, 40 A, 36 V/ 13 A and 48 V/ 10 A, 20 A
- Extremely slim design no lateral installation clearances required
- Power boost with 3 times rated current (for 25 ms) for tripping protective devices
- Extra power with 1.5 times rated current (5 s/min) for brief functional overload
- Selectable short-circuit response between constant current and restart
- Symmetrical load distribution can be selected for parallel operation
- Operating state on 3 LEDs
- Extremely high efficiency up to 94%
- Wide temperature range from -25 to +70 °C
- Comprehensive certifications, such as cULus, ATEX, IECex and DNV GL

2

### Advanced power supplies

SITOP PSU8200

#### Overview



The 1-phase SITOP modular are technology power supplies for sophisticated solutions and offer maximum functionality for use in complex plants and machines. The wide-range input allows a connection to almost any electrical power system worldwide and ensures a high degree of safety even if there are large voltage fluctuations. The power boost provides up to three times the rated current for brief periods. In case of overload, you can choose between constant current with automatic restart or latching shutdown. The high degree of efficiency keeps energy consumption and heating in the control cabinet low, and the compact metal housing also saves space.

To further increase the 24 V availability, the SITOP modular power supplies can be combined with **buffer**, **DC UPS**, **redundancy** and **selectivity modules**.

#### Main product highlights

- 24 V DC/ 5 A, 10 A, 20 A and 40 A
- 1-phase wide-range input for connection to any supply system and for safety in case of voltage supply deviations
- Extremely slim design no lateral installation clearances required
- Power Boost with 3 times the rated current (for 25 ms) for tripping protective devices
- Extra power with 1.5 times the rated current (5 s/min) for brief functional overload
- Selectable short-circuit response between constant current and restart
- Optional symmetrical load distribution for parallel operation
- Operating status on 3 LEDs
- Extremely high efficiency to 94 %
- Wide temperature range from -25 to +70 °C
- Comprehensive certifications, such as cULus, ATEX and DNV GL

Technical speci	ifications
-----------------	------------

Article number	6EP3333-8SB00-0AY0	6EP3334-8SB00-0AY0	6EP1336-3BA10	6EP3337-8SB00-0AY0
Product	SITOP PSU8200	SITOP PSU8200	SITOP PSU8200	SITOP PSU8200
Power supply, type	24 V/5 A	24 V/10 A	24 V/20 A	24 V/40 A
Input				
Input	1-phase AC	1-phase AC	1-phase AC or DC	1-phase AC
Rated voltage V <sub>in rated</sub>	-	-	120 230 V	-
Voltage range AC	-	-	85 275 V	-
Note	Automatic range selection	Automatic range selection	Derating of temperature necessary down to 50 °C at V <sub>in</sub> < 100 V AC or DC	Automatic selection; startup starting from $U_{\rm e} \ge 90/180 \text{ V}$
Supply voltage				
<ul> <li>1 at AC Rated value</li> </ul>	120 V	120 V		120 V
<ul> <li>2 at AC Rated value</li> </ul>	230 V	230 V		230 V
• at DC	-	-	110 220 V	-
Input voltage				
• 1 at AC	85 132 V	85 132 V	-	85 132 V
• 2 at AC	170 264 V	170 264 V		170 264 V
• at DC	-	-	88 350 V	-
Wide-range input	No	No	Yes	No
Mains buffering at Iout rated, min.	35 ms; at V <sub>in</sub> = 120/230 V	35 ms; at V <sub>in</sub> = 120/230 V	20 ms; at V <sub>in</sub> = 230 V	25 ms; at V <sub>in</sub> = 230 V
Rated line frequency 1	50 Hz	50 Hz	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz	45 65 Hz	45 65 Hz

1-phase, 24 V DC

Article number Product	6EP3333-8SB00-0AY0 SITOP PSU8200	6EP3334-8SB00-0AY0 SITOP PSU8200	6EP1336-3BA10 SITOP PSU8200	6EP3337-8SB00-0AY0 SITOP PSU8200
Power supply, type	24 V/5 A	24 V/10 A	24 V/20 A	24 V/40 A
nput (continued)				
Input current				
<ul> <li>at rated input voltage 120 V</li> </ul>	2.1 A	4 A	4.6 A	15 A
<ul> <li>at rated input voltage 230 V</li> </ul>	1.2 A	1.9 A	2.5 A	9 A
Switch-on current limiting (+25 °C), max.	10 A	10 A	20 A	60 A
l²t, max.	0.2 A <sup>2</sup> ·s	0.3 A <sup>2</sup> ·s	5 A <sup>2</sup> ·s	8 A <sup>2</sup> ·s
Built-in incoming fuse	T 3.15 A (not accessible)	T 6.3 A (not accessible)	Yes	Yes
Protection in the mains power input (IEC 898)	at 2-phase operation: circuit breaker 2-pole connected or circuit breaker 3RV2011-1EA10 (setting 3.8 A) or 3RV2711-1ED10 (UL 489) at 230 V; 3RV2011-1DA10 (setting 3 A)	Recommended miniature circuit breaker at 1-phase operation: from 6 A (10 A) characteristic C (B); required at 2-phase operation: circuit breaker 2-pole connected or circuit breaker 3RV2011-1EA10 (setting 3.8 A) or 3RV2711-1ED10 (UL 489) at 230 V; 3RV2011-1DA10 (setting 3.A) or 3RV2711-1DD10 (UL 489) at 400/500 V	operation: circuit breaker 2-pole connected or circuit breaker 3RV2711-1HD10 (UL 489) at 120 V or 3RV2711-1ED10 (UL 489)	Recommended miniature circuit breaker at 1-phass operation: 16 A characte istic C; required at 2-pha operation: circuit breaker 2-pole connected or circu breaker 3RV2421-4BA10 (120 V) or 3RV2411-1JA10 (230 V)
Dutput				
Output	Controlled, isolated DC	Controlled, isolated DC	Controlled, isolated DC	Controlled, isolated DC
	voltage	voltage	voltage	voltage
Rated voltage V <sub>out rated</sub> DC	24 V	24 V	24 V	24 V
Total tolerance, static $\pm$	3 %	3 %	3 %	3 %
Static mains compensation, approx.	0.1 %	0.1 %	0.1 %	0.1 %
Static load balancing, approx.	0.2 %	0.3 %	0.3 %	0.1 %
Residual ripple peak-peak, max.	50 mV	50 mV	100 mV	100 mV
Residual ripple peak-peak, typ.			80 mV	50 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV	200 mV	200 mV	240 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)			100 mV	220 mV
Adjustment range	24 28.8 V	24 28.8 V	24 28.8 V	24 28 V
Product function Output voltage adjustable	Yes	Yes	Yes	Yes
Output voltage setting	via potentiometer; max. 120 W	via potentiometer; max. 240 W	via potentiometer	via potentiometer; max. 960 W
Status display	Green LED for 24 V OK	Green LED for 24 V OK	Green LED for 24 V OK	Green LED for 24 V OK; L yellow for overload; LED for short-circuit or latchin shutdown
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact rating 60 V DC/ 0.3 A) for "24 V OK"
On/off behavior	Overshoot of V <sub>out</sub> approx. 3 %	Overshoot of V <sub>out</sub> approx. 3 %	Overshoot of V <sub>out</sub> approx. 3 %	Overshoot of V <sub>out</sub> approx 3 %
Startup delay, max.	1.5 s	1.5 s	1.5 s	1.5 s
Voltage rise, typ.	30 ms	70 ms	50 ms	30 ms
Rated current value I <sub>out rated</sub>	5 A	10 A	20 A	40 A
Current range	0 5 A	0 10 A	0 20 A	0 40 A
• Note	As of <i>U</i> <sub>a</sub> >24 V: 4% [ <i>I</i> <sub>a</sub> ]/V [ <i>U</i> <sub>a</sub> ]; at <i>U</i> <sub>e</sub> <100 V/<200 V: 80% <i>I</i> <sub>a rated</sub>	+60 +70 °C: Derating 2%/K; as of $U_a > 24$ V: 4% $[I_a]/V [U_a];$ at $U_e$ 100 V/<200 V: 80% $I_a$ rated	+60 +70 °C: Derating 3%/K	+60 +70 °C: Derating 3%/K
Supplied active power typical Short-term overload current	120 W	240 W	480 W	960 W
<ul> <li>on short-circuiting during the start- up typical</li> </ul>	-		-	120 A
· · · · ·				

# Advanced power supplies SITOP PSU8200

## 1-phase, 24 V DC

## Technical specifications (continued)

6EP3333-8SB00-0AY0	6EP3334-8SB00-0AY0	6EP1336-3BA10	
			6EP3337-8SB00-0AY0
SITOP PSU8200	SITOP PSU8200	SITOP PSU8200	SITOP PSU8200
24 V/5 A	24 V/10 A	24 V/20 A	24 V/40 A
			05
-	-	-	25 ms
25 ms	25 ms	25 ms	25 ms
6 A	12 A	30 A	60 A
Yes; switchable characteristic	Yes; switchable characteristic	Yes; switchable characteristic	Yes; switchable characteristic
2	2	2	2
93 %	94 %	93 %	92 %
9 W	18 W	42 W	82 W
1.5 W	1.5 W	-	6.8 W
0.1 %	0.1 %	0.5 %	1 %
2 %	4 %	1 %	1.9 %
0.25 ms	0.25 ms	1 ms	2 ms
0.5 ms	0.5 ms	1 ms	2 ms
2 %	4 %	-	3.8 %
. 0.25 ms	0.25 ms	-	1 ms
	0.5 ms	-	1 ms
1 ms	1 ms	5 ms	1 ms
< 33 V	< 33 V	< 33 V	< 32 V
6 A	12 A	21.5 A	41 A
Yes	Yes	Yes	Yes
Alternatively, constant current characteristic approx. 6 A or latching shutdown	Alternatively, constant current characteristic approx. 12 A or latching shutdown	Alternatively, constant current characteristic approx. 23 A or latching shutdown	Alternatively, constant current characteristic approx. 41 A or latching shutdown
<b>.</b> .	10.4		
			41 A
overload capability 150 % I <sub>out rated</sub> up to 5 s/min	overload capability 150 % I <sub>out rated</sub> up to 5 s/min	overload capability 150 % I <sub>out rated</sub> up to 5 s/min	250% <i>I</i> <sub>out rated</sub> up to 25 ms, 150% <i>I</i> <sub>out rated</sub> up to 5 s/min
LED yellow for "overload", LED red for "latching shutdown"	LED yellow for "overload", LED red for "latching shutdown"	LED yellow for "overload", LED red for "latching shutdown"	LED yellow for "overload", LED red for "latching shutdown" or "short-circuit"
Yes	Yes	Yes	Yes
Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178
Class I	Class I	Class I	Class I
3.5 mA	3.5 mA	3.5 mA	0.1 mA
1 mA	1 mA	1 mA	0.1 mA
Yes	Yes	Yes	Yes
cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1,	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1,	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1,	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
	24 V/5 A           -           25 ms           6 A           Yes; switchable characteristic 2           93 %           9 W           1.5 W           0.1 %           2 %           0.25 ms           0.5 ms           2 %           0.25 ms           0.5 ms           1 ms           < 33 V	24 V/5 A24 V/10 A25 ms-25 ms25 ms6 A12 AYes; switchable characteristic 2Yes; switchable characteristic 293 %94 %9 W18 W1.5 W1.5 W0.1 %0.1 %2 %4 %0.25 ms0.25 ms0.5 ms0.5 ms2 %4 %0.25 ms0.5 ms0.5 ms0.5 ms1 ms1 ms< 33 V	24 VIS A24 VITO A24 VIZO A25 ms25 ms25 ms25 ms25 ms25 ms6 A12 A30 AYes; switchable characteristic 2293 %94 %93 %9W18 W42 W1.5 W1.5 W-0.1 %0.1 %0.5 %2%0.1 %0.5 %2%0.1 %0.5 %0.1 %0.25 ms1 ms0.25 ms0.25 ms1 ms0.5 ms0.5 ms1 ms2%4 %-0.5 ms0.5 ms1 ms0.5 ms0.5 ms-0.5 ms0.5 ms-1 ms5 ms-2%4 %-0.4 A12 A21.5 AYesYesYesAlternatively, constant outrated up to 5 s/minAlternatively, constant outrated up to 5 s/min6 A operioad capability 150 % outrated up to 5 s/min23 A6 A outrated up to 5 s/minLED yellow for 'overload', ED red for 'taching shutdown'1ED red for 'taching shutdown'-1ED red for 'taching shutdown'-1ED red for 'taching shutdown'-YesSata-Sata- <td< td=""></td<>

1-phase, 24 V DC

Article number	6EP3333-8SB00-0AY0	6EP3334-8SB00-0AY0	6EP1336-3BA10	6EP3337-8SB00-0AY0
Product	SITOP PSU8200	SITOP PSU8200	SITOP PSU8200	SITOP PSU8200
Power supply, type	24 V/5 A	24 V/10 A	24 V/20 A	24 V/40 A
Safety (continued)				
Explosion protection	T4 Gc; cĆSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01)	T4 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01)	IECEX EX NA NC IIC T3 GC; ATEX (EX) II 3G EX NA NC IIC T3 GC; cCSAUs (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T3	T3; cULus (Hazloc) Class Div. 2, Group ABCD, T3;
FM approval	-	-	-	-
CB approval	Yes	Yes	Yes	Yes
Marine approval	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20
EMC				
Emitted interference	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2	EN 61000-3-2	EN 61000-3-2	
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data				
Ambient temperature				
during operation	-25 +70 °C	-25 +70 °C	-25 +70 °C	-25 +70 °C
- Note	With natural convection;	With natural convection;	With natural convection;	with natural convection
- Note	startup tested starting from - 40 °C nominal voltage	startup tested starting from - 40 °C nominal voltage	startup tested starting from - 40 °C nominal voltage	with hatural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics				
Connection technology Connections	screw-type terminals	screw-type terminals	screw-type terminals	screw-type terminals
<ul> <li>Supply input</li> </ul>	L, N, PE: 1 screw terminal each for 0.2 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.2 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.2 4 mm <sup>2</sup> single- core/finely stranded	L, N, PE: 1 screw termina each for 0.2 4 mm <sup>2</sup> sin core/finely stranded
• Output	+, -: 2 screw terminals each for 0.2 2.5 $\mbox{mm}^2$	+, -: 2 screw terminals each for 0.2 2.5 mm <sup>2</sup>	+, -: 2 screw terminals each for 0.2 4 $\text{mm}^2$	+, -: 2 screw terminals ea for 0.5 10 mm <sup>2</sup>
• Auxiliary	13, 14 (alarm signal): 1 screw terminal each for 0.14 1.5 mm <sup>2</sup> ; 15, 16 (Remote): 1 screw terminal each for 0.14 1.5 mm <sup>2</sup>	13, 14 (alarm signal): 1 screw terminal each for 0.14 1.5 mm <sup>2</sup> ; 15, 16 (Remote): 1 screw terminal each for 0.14 1.5 mm <sup>2</sup>	13, 14 (alarm signal): 1 screw terminal each for 0.14 1.5 mm <sup>2</sup>	13, 14 (alarm signal): 1 screw terminal each fo 0.14 1.5 mm <sup>2</sup>
Width of the enclosure	45 mm	55 mm	90 mm	145 mm
Height of the enclosure	125 mm	125 mm	125 mm	145 mm
Depth of the enclosure	125 mm	125 mm	125 mm	150 mm
Required spacing				
• top	50 mm	50 mm	50 mm	40 mm
• bottom	50 mm	50 mm	50 mm	40 mm
• left	0 mm	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm	0 mm
Weight, approx.	0.8 kg	1 kg	1.2 kg	3.1 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x15
Electrical accessories	Buffer module	Buffer module	Buffer module	Buffer module, redundar module
Mechanical accessories	Device identification label 20 mm × 7 mm, Tl-grey 3RT2900-1SB20	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification labe 20 mm × 7 mm, TI-grey 3RT2900-1SB20
MTBF at 40 °C	1 421 519 h	1 292 102 h	667 048 h	838 156 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated in voltage and ambient temperature +25 °C (unle otherwise specified)

2

# Advanced power supplies SITOP PSU8200

ohase, 24 V DC			
Ordering data	Article No.	Accessories	Article No.
SITOP PSU8200 1-phase, 24 V DC/5 A	6EP3333-8SB00-0AY0	SITOP redundancy modules	see page 9/6
		SITOP selectivity modules	see page 9/14
Stabilized power supply nput: 120/230 V AC		SITOP buffer modules	see page 9/16
Output: 24 V DC/5 A		SITOP DC UPS	see page 8/2
SITOP PSU8200 1-phase, 24 V DC/10 A	6EP3334-8SB00-0AY0	Device identification label	3RT2900-1SB20
Stabilized power supply Input: 120/230 V AC Output: 24 V DC/10 A			
SITOP PSU8200, 1-phase, 24 V DC/20 A	6EP1336-3BA10		
Stabilized power supply Input: 120 230 V AC/110-220 V DC Output: 24 V DC/20 A			
SITOP PSU8200 1-phase, 24 V DC/40 A	6EP3337-8SB00-0AY0		
Stabilized power supply Input: 120/230 V AC Output: 24 V DC/40 A			

2

#### Overview



The 1-phase and 2-phase SITOP modular are technology power supplies for sophisticated solutions and offer maximum functionality for use in complex plants and machines. The ultra-wide input range allows connections to almost any 1-phase power supply system or directly between the line conductors of threephase networks (2-phase) and ensures a high degree of safety even if there are large voltage fluctuations. The power boost provides up to three times the rated current for brief periods. In case of overload, you can choose between constant current with automatic restart or latching shutdown. The high degree of efficiency keeps energy consumption and heating in the control cabinet low, and the compact metal housing also saves space.

To further increase 24 V availability, the SITOP modular power supplies can be combined with **buffer**, **DC UPS**, **redundancy** and **selectivity modules**.

#### Main product highlights

- 24 V/5 A and 10 A, also available as version with PCB with protective coating.
- 1-phase and 2-phase ultra-wide input range
- Extremely slim design no lateral installation clearances required
- Power Boost with 3 times the rated current (for 25 ms) for tripping protective devices
- Extra power with 1.5 times the rated current (5 s/min) for brief functional overload
- Selectable short-circuit response between constant current and restart
- · Optional symmetrical load distribution for parallel operation
- Operating status on 3 LEDs
- High degree of efficiency up to 91 %
- Wide temperature range from -25 to +70 °C
- Comprehensive certifications, such as cULus, ATEX and DNV GL

Article number Product	6EP1333-3BA10 SITOP PSU200M	6EP1333-3BA10-8AC0 SITOP PSU200M Protective coating	6EP1334-3BA10 SITOP PSU200M	6EP1334-3BA10-8AB0 SITOP PSU200M Protective coating
Power supply, type	24 V/5 A	24 V/5 A	24 V/10 A	24 V/10 A
Input				
Input	1-phase and 2-phase AC	1-phase and 2-phase AC	1-phase and 2-phase AC	1-phase and 2-phase AC
• Note	Set by means of selector switch on the device; starting from $V_{in} > 90/180 \text{ V}$	Set by means of selector switch on the device; starting from $V_{in} > 90/180$ V	Set by means of selector switch on the device	Set by means of selector switch on the device
Supply voltage				
• 1 at AC	120 230 V	120 230 V	120 230 V	120 230 V
• 2 at AC	230 500 V	230 500 V	230 500 V	230 500 V
Input voltage				
• 1 at AC	85 264 V	85 264 V	85 264 V	85 264 V
• 2 at AC	176 550 V	176 550 V	176 550 V	176 550 V
Wide-range input	Yes	Yes	Yes	Yes
Overvoltage resistance	1300 V <sub>peak</sub> , 1.3 ms	1300 V <sub>peak</sub> , 1.3 ms	1300 V <sub>peak</sub> , 1.3 ms	1300 V <sub>peak</sub> , 1.3 ms
Mains buffering at I <sub>out rated</sub> , min.	25 ms; at $V_{in} = 120/230$ V, typ. 150 ms at $V_{in} = 400$ V	25 ms; at $V_{in} = 120/230$ V, typ. 150 ms at $V_{in} = 400$ V	25 ms; at $V_{in}$ = 120/230 V, typ. 150 ms at $V_{in}$ = 400 V	25 ms; at V <sub>in</sub> = 120/230 V, typ. 150 ms at V <sub>in</sub> = 400 V
Rated line frequency 1	50 Hz	50 Hz	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz	47 63 Hz	47 63 Hz
Input current				
<ul> <li>at rated input voltage 120 V</li> </ul>	2.2 A	2.2 A	4.4 A	4.4 A
<ul> <li>at rated input voltage 230 V</li> </ul>	1.2 A	1.2 A	2.4 A	2.4 A
<ul> <li>at rated input voltage 500 V</li> </ul>	0.61 A	0.61 A	1.1 A	1.1 A

#### Technical specifications

# Advanced power supplies

SITOP PSU8200

# 1- and 2-phase, 24 V DC

## Technical specifications (continued)

Article number	6EP1333-3BA10	6EP1333-3BA10-8AC0	6EP1334-3BA10	6EP1334-3BA10-8AB0
Product	SITOP PSU200M	SITOP PSU200M Protective coating	SITOP PSU200M	SITOP PSU200M Protective coating
Power supply, type	24 V/5 A	24 V/5 A	24 V/10 A	24 V/10 A
Input (continued)				
Switch-on current limiting (+25 °C), max.	35 A	35 A	35 A	35 A
l²t, max.	1.7 A <sup>2</sup> ·s	1.7 A <sup>2.</sup> s	4 A <sup>2</sup> ·s	4 A <sup>2</sup> ·s
Built-in incoming fuse	T 3.15 A (not accessible)	T 3.15 A (not accessible)	T 6.3 A (not accessible)	T 6.3 A (not accessible)
Protection in the mains power input (IEC 898)	at 2-phase operation: circuit	Recommended miniature circuit breaker at 1-phase operation: from 6 A (10 A) characteristic C (B); required at 2-phase operation: circuit breaker 2-pole connected or circuit breaker 3RV2011-1EA10 (setting 3.8 A) or 3RV2711-1ED10 (UL 489) at 230 V; 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489) at 400/500 V	at 2-phase operation: circuit	at 2-phase operation: circuit
Output				
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage Vout rated DC	24 V	24 V	24 V	24 V
Total tolerance, static $\pm$	3 %	3 %	3 %	3 %
Static mains compensation, approx.	0.1 %	0.1 %	0.1 %	0.1 %
Static load balancing, approx.	0.1 %	0.1 %	0.1 %	0.1 %
Residual ripple peak-peak, max.	50 mV	50 mV	50 mV	50 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV	200 mV	200 mV	200 mV
Adjustment range	24 28.8 V	24 28.8 V	24 28.8 V	24 28.8 V
Product function Output voltage adjustable	Yes	Yes	Yes	Yes
Output voltage setting	via potentiometer	via potentiometer	via potentiometer	via potentiometer
Status display	Green LED for 24 V OK	Green LED for 24 V OK	Green LED for 24 V OK	Green LED for 24 V OK
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"
On/off behavior	Overshoot of V <sub>out</sub> approx. 3 %	Overshoot of V <sub>out</sub> approx. 3 %	Overshoot of $V_{out}$ approx. 3 %	Overshoot of V <sub>out</sub> approx. 3 %
Startup delay, max.	1 s	1 s	1 s	1 s
Voltage rise, typ.	50 ms	50 ms	50 ms	50 ms
Rated current value Iout rated	5 A	5 A	10 A	10 A
Current range	0 5 A	0 5 A	0 10 A	0 10 A
Note	-	-	+60 +70 °C: Derating 2%/K (at 120 V, 230 V) or 3.5%/K (at 400 V)	+60 +70 °C: Derating 2%/K (at 120 V, 230 V) or 3.5%/K (at 400 V)
Supplied active power typical Short-term overload current	120 W	120 W	240 W	240 W
<ul> <li>at short-circuit during operation typical</li> </ul>	15 A	15 A	30 A	30 A
Duration of overloading capability for excess current				
<ul> <li>at short-circuit during operation</li> </ul>	25 ms	25 ms	25 ms	25 ms
Constant overload current				
• on short-circuiting during the start- up typical	6 A	6 A	12 A	12 A
Parallel switching for enhanced performance	Yes; switchable characteristic	Yes; switchable characteristic	Yes; switchable characteristic	Yes; switchable characteristic
Numbers of parallel switchable units for enhanced performance	2	2	2	2

1- and 2-phase, 24 V DC

Article number	6EP1333-3BA10	6EP1333-3BA10-8AC0	6EP1334-3BA10	6EP1334-3BA10-8AB0
Product	SITOP PSU200M	SITOP PSU200M Protective coating	SITOP PSU200M	SITOP PSU200M Protective coating
Power supply, type	24 V/5 A	24 V/5 A	24 V/10 A	24 V/10 A
Efficiency				
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	88 %	88 %	91 %	91 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	17 W	17 W	24 W	24 W
Power loss [W] during no-load operation maximum	4 W	4 W	6 W	6 W
Closed-loop control				
Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	0.1 %	0.1 %	0.1 %	0.1 %
Dynamic load smoothing $(I_{out}: 50/100/50 \%), U_{out} \pm typ.$	3 %	3 %	3 %	3 %
Load step setting time 50 to 100%, typ.	2 ms	2 ms	2 ms	2 ms
Load step setting time 100 to 50%, typ.	2 ms	2 ms	2 ms	2 ms
Setting time maximum	5 ms	5 ms	5 ms	5 ms
Protection and monitoring				
Output overvoltage protection	< 35 V	< 35 V	< 35 V	< 35 V
Current limitation, typ.	6 A	6 A	12 A	12 A
Property of the output Short-circuit proof	Yes	Yes	Yes	Yes
Short-circuit protection	Alternatively, constant current characteristic approx. 5.5 A or latching shutdown	Alternatively, constant current characteristic approx. 5.5 A or latching shutdown	Alternatively, constant current characteristic approx. 12 A or latching shutdown	Alternatively, constant current characteristic approx. 12 A or latching shutdown
Enduring short circuit current RMS value				
typical	6 A	6 A	12 A	12 A
Overload/short-circuit indicator	LED yellow for "overload", LED red for "latching shutdown"	LED yellow for "overload", LED red for "latching shutdown"	LED yellow for "overload", LED red for "latching shutdown"	LED yellow for "overload LED red for "latching shutdown"
Safety				
Primary/secondary isolation	Yes	Yes	Yes	Yes
Galvanic isolation	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 501
Protection class	Class I	Class I	Class I	Class I
Leakage current				
• maximum	3.5 mA	3.5 mA	3.5 mA	3.5 mA
• typical	0.25 mA	0.25 mA	0.32 mA	0.32 mA
CE mark	Yes	Yes	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	CULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259, cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
Explosion protection	T4 Gc (für AC 120-230/230- 400 V); cCSAus (CSA C22.2	T4 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD,	IECEX EX NA NC IIC T4 Gc; ATEX (EX) II 3G EX NA NC IIC	T4 Gc; cCSAus (CSA C2 No. 213, ANSI/ISA-12.12
FM approval	-	-	-	-
CB approval	Yes	No	Yes	No
Marine approval	GL, ABS	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20
EMC		11 20		
Emitted interference	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2	EN 61000-3-2	EN 61000-3-2	EN 61000-3-2

# Advanced power supplies SITOP PSU8200

# 1- and 2-phase, 24 V DC

## Technical specifications (continued)

Article number	6EP1333-3BA10	6EP1333-3BA10-8AC0	6EP1334-3BA10	6EP1334-3BA10-8AB0
Product	SITOP PSU200M	SITOP PSU200M Protective coating	SITOP PSU200M	SITOP PSU200M Protective coating
Power supply, type	24 V/5 A	24 V/5 A	24 V/10 A	24 V/10 A
Operating data				
Ambient temperature				
<ul> <li>during operation</li> </ul>	-25 +70 °C	-25 +70 °C	-25 +70 °C	-25 +70 °C
- Note	With natural convection; startup tested starting from - 40 °C nominal voltage	with natural convection	With natural convection; startup tested starting from - 40 °C nominal voltage	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation			
Mechanics				
Connection technology	screw-type terminals	screw-type terminals	screw-type terminals	screw-type terminals
Connections				
Supply input	L, N, PE: 1 screw terminal each for 0.2 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.2 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.2 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.2 2.5 mm <sup>2</sup> single-core/finely stranded
Output	+, -: 2 screw terminals each for 0.2 2.5 $\mbox{mm}^2$	+, -: 2 screw terminals each for 0.2 2.5 $\mbox{mm}^2$	+, -: 2 screw terminals each for 0.2 2.5 $\mbox{mm}^2$	+, -: 2 screw terminals each for 0.2 2.5 mm <sup>2</sup>
Auxiliary	13, 14 (alarm signal): 1 screw terminal each for 0.14 1.5 mm <sup>2</sup>	13, 14 (alarm signal): 1 screw terminal each for 0.14 1.5 mm <sup>2</sup>	13, 14 (alarm signal): 1 screw terminal each for 0.14 1.5 mm <sup>2</sup>	13, 14 (alarm signal): 1 screw terminal each for 0.14 1.5 mm <sup>2</sup>
Width of the enclosure	70 mm	70 mm	70 mm	70 mm
Height of the enclosure	125 mm	125 mm	125 mm	125 mm
Depth of the enclosure	121 mm	121 mm	121 mm	121 mm
Required spacing				
• top	50 mm	50 mm	50 mm	50 mm
<ul> <li>bottom</li> </ul>	50 mm	50 mm	50 mm	50 mm
• left	0 mm	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm	0 mm
Weight, approx.	0.6 kg	0.6 kg	0.8 kg	0.8 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15			
Electrical accessories	Buffer module	Buffer module	Buffer module	Buffer module
MTBF at 40 °C	1 123 973 h	1 123 973 h	1 055 408 h	1 055 408 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

# Advanced power supplies SITOP PSU8200

1- and 2-phase, 24 V DC

data	Article No.	Accessories	Article No.
P PSU200M 1-phase and	6EP1333-3BA10	SITOP redundancy modules	see page 9/6
phase, 24 V DC/5 A		SITOP selectivity modules	see page 9/14
abilized power supply put: 120 230/230 500 V AC		SITOP buffer modules	see page 9/16
itput: 24 V DC/5 A		SITOP DC UPS	see page 8/2
TOP modular 1-phase and phase, 24 V DC /5 A	6EP1333-3BA10-8AC0	Device identification label	3RT2900-1SB20
abilized power supply put: 120 230/230 500 V AC utput: 24 V DC/5 A rrsion with protective coating			
FOP PSU200M 1-phase and bhase, 24 V DC/10 A	6EP1334-3BA10		
abilized power supply put: 120 230 /230 500 V AC utput: 24 V DC / 10 A			
ITOP modular 1-phase and -phase, 24 V DC /10 A	6EP1334-3BA10-8AB0		
abilized power supply put: 120 230/230 500 V AC utput: 24 V DC/10 A rsion with protective coating			

## Advanced power supplies

SITOP PSU8200

Technical specifications

#### Overview



The 3-phase SITOP modular are technology power supplies for sophisticated solutions and offer maximum functionality for use in complex plants and machines. The wide-range input allows a connection to almost any electrical power system worldwide and ensures a high degree of safety even if there are large voltage fluctuations. The power boost provides up to three times the rated current for brief periods. In case of overload, you can choose between constant current with automatic restart or latching shutdown. The high degree of efficiency keeps energy consumption and heating in the control cabinet low, and the compact metal housing also saves space.

To further increase 24 V availability, the SITOP modular power supplies can be combined with **buffer**, **DC UPS**, **redundancy** and **selectivity modules**.

#### Main product highlights

- 24 V DC/ 20 A and 40 A
- 3-phase wide-range input from 320 to 575 V AC for global use
- Extremely slim design no lateral installation clearances required
- Power Boost with 3 times the rated current (for 25 ms) for tripping protective devices
- Extra power with 1.5 times the rated current (5 s/min) for brief functional overload
- Selectable short-circuit response between constant current
   and restart
- Optional symmetrical load distribution for parallel operation
- Operating status on 3 LEDs
- Extremely high efficiency up to 94%
- Wide temperature range from -25 to +70 °C
- Comprehensive certifications, such as cULus, ATEX, IECex, Class1 Div2 and DNV GL

Article number	6EP3436-8SB00-0AY0	6EP3437-8SB00-0AY0
Product	SITOP PSU8200	SITOP PSU8200
Power supply, type	24 V/20 A	24 V/40 A
Input		
Input	3-phase AC	3-phase AC
Rated voltage value V <sub>in rated</sub>	400 500 V	400 500 V
Voltage range AC	320 575 V	320 575 V
Wide-range input	Yes	Yes
Mains buffering at Iout rated, min.	15 ms; at V <sub>in</sub> = 400 V	10 ms; at V <sub>in</sub> = 400 V
Rated line frequency 1	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz
Rated line range	47 63 Hz	45 65 Hz
Input current		
<ul> <li>at rated input voltage 400 V</li> </ul>	1.2 A	2.1 A
<ul> <li>at rated input voltage 500 V</li> </ul>	1 A	1.7 A
Switch-on current limiting (+25 °C), max.	16 A	13 A
l²t, max.	0.8 A <sup>2</sup> ·s	2.24 A <sup>2.</sup> s
Built-in incoming fuse	none	none
Protection in the mains power input (IEC 898)	Required: 3-pole connected miniature circuit breaker 6 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)	Required: 3-pole connected miniature circuit breaker 10 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)

Advanced power supplies SITOP PSU8200

3-phase, 24 V DC

Article number	6EP3436-8SB00-0AY0	6EP3437-8SB00-0AY0	
Product	SITOP PSU8200	SITOP PSU8200	
Power supply, type	24 V/20 A	24 V/40 A	
Output			
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage	
Rated voltage Vout rated DC	24 V	24 V	
Total tolerance, static ±	3 %	3 %	
Static mains compensation, approx.	0.1 %	0.1 %	
Static load balancing, approx.	0.2 %	0.2 %	
Residual ripple peak-peak, max.	100 mV	100 mV	
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV	240 mV	
Adjustment range	24 28 V	24 28 V	
Product function Output voltage adjustable	Yes	Yes	
Output voltage setting	via potentiometer; max. 480 W	via potentiometer; max. 960 W	
Status display	Green LED for 24 V OK	Green LED for 24 V OK	
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	
On/off behavior	No overshoot of V <sub>out</sub> (soft start)	minimal overshooting (< 2 %)	
Startup delay, max.	2.5 s	0.1 s	
Voltage increase time of the output voltage maximum	500 ms	100 ms	
Rated current value Iout rated	20 A	40 A	
Current range	0 20 A	0 40 A	
Note	+60 +70 °C: Derating 2%/K	+60 +70 °C: Derating 4%/K	
Supplied active power typical	480 W	960 W	
Short-term overload current			
<ul> <li>at short-circuit during operation typical</li> </ul>	60 A	120 A	
Duration of overloading capability for excess current			
at short-circuit during operation	25 ms	25 ms	
Constant overload current			
<ul> <li>on short-circuiting during the start- up typical</li> </ul>	22 A	44 A	
Parallel switching for enhanced performance	Yes; switchable characteristic	Yes; switchable characteristic	
Numbers of parallel switchable units for enhanced performance	2	2	
Efficiency			
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	94 %	94 %	
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	31 W	66 W	
Power loss [W] during no-load operation maximum		4 W	
Closed-loop control			
Dynamic mains compensation ( <i>V</i> <sub>in rated</sub> ±15 %), max.	0.1 %	1 %	
Dynamic load smoothing (I <sub>out</sub> : 50/100/ 50 %), U <sub>out</sub> ± typ.	1 %	3 %	
Load step setting time 50 to 100%, typ.	0.2 ms	-	
Load step setting time 100 to 50%, typ.	0.2 ms	-	
Dynamic load smoothing (I <sub>out</sub> : 10/90/ 10 %), U <sub>out</sub> ± typ.	2 %	-	
Load step setting time 10 to 90%, typ.	0.2 ms	-	
Load step setting time 90 to 10%, typ.		-	
Setting time maximum	10 ms	10 ms	

# Technical specifications (continued)

# Advanced power supplies SITOP PSU8200

# 3-phase, 24 V DC

## Technical specifications (continued)

	,	
Article number	6EP3436-8SB00-0AY0	6EP3437-8SB00-0AY0
Product	SITOP PSU8200	SITOP PSU8200
Power supply, type	24 V/20 A	24 V/40 A
Protection and monitoring	20.1/	01.0.1/
Output overvoltage protection	< 32 V	< 31.8 V
Current limitation, typ.	22 A	44 A
Property of the output Short-circuit proof	Yes	Yes
Short-circuit protection	Alternatively, constant current characteristic approx. 22 A or latching shutdown	Alternatively, constant current characteristic approx. 44 A or latching shutdown
Enduring short circuit current RMS value		
<ul> <li>typical</li> </ul>	22 A	50 A
Overcurrent overload capability in normal operation	overload capability 150 % I <sub>out rated</sub> up to 5 s/min	overload capability 150 % lout rated up to 5 s/min
Overload/short-circuit indicator	LED yellow for "overload", LED red for "latching shutdown"	LED yellow for "overload", LED red for "latching shutdown"
Safety		
Primary/secondary isolation	Yes	Yes
Galvanic isolation	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178
Protection class	Class I	Class I
Leakage current		
• maximum	3.5 mA	1 mA
<ul> <li>typical</li> </ul>	0.9 mA	0.6 mA
CE mark	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
Explosion protection	IECEX EX NA NC IIC T4 Gc; ATEX (EX) II 3G EX NA NC IIC T4 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4
FM approval	-	-
CB approval	Yes	Yes
Marine approval	ABS, DNV GL	ABS, DNV GL
Degree of protection (EN 60529)	IP20	IP20
EMC		
Emitted interference	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2
Operating data		
Ambient temperature		
<ul> <li>during operation</li> </ul>	-25 +70 °C	-25 +70 °C
- Note	With natural convection; startup tested starting from -40 °C nominal voltage	With natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics		
Connection technology	screw-type terminals	screw-type terminals
Connections		
<ul> <li>Supply input</li> </ul>	L1, L2, L3, PE: 1 screw terminal each for 0.2 4 mm <sup>2</sup> single-core/finely stranded	L1, L2, L3, PE: 1 screw terminal each for 0.5 4 mm <sup>2</sup> single-core/finely stranded
Output	+, -: 2 screw terminals each for 0.2 4 mm <sup>2</sup>	+: 2 screw terminals each for 0.5 16 mm <sup>2</sup> ; -: 3 screw terminals each for 0.5 16 mm <sup>2</sup>
Auxiliary	13, 14 (alarm signal): 1 screw terminal each for 0.14 1.5 mm²; 15, 16 (Remote): 1 screw terminal each for 0.14 1.5 mm²	13, 14 (alarm signal), 15, 16 (Remote): 1 screw terminal each for 0.05 2.5 mm <sup>2</sup>
Width of the enclosure	70 mm	135 mm
Height of the enclosure	125 mm	145 mm
Depth of the enclosure	125 mm	150 mm

3-phase, 24 V DC

Article number	6EP3436-8SB00-0AY0	6EP3437-8SB00-0AY0
Product	SITOP PSU8200	SITOP PSU8200
Power supply, type	24 V/20 A	24 V/40 A
Required spacing		
• top	50 mm	40 mm
• bottom	50 mm	40 mm
• left	0 mm	0 mm
• right	0 mm	0 mm
Weight, approx.	1.2 kg	3.3 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x15
Electrical accessories	Buffer module	Buffer module
Mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20
MTBF at 40 °C	590 573 h	517 015 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
Ordering data	Article No.	sories Article No.
		adundanov modulos

#### SITOP PSU8200, 3-phase, 24 V DC/20 A 6EP3436-8SB00-0AY0 SITOP redundancy modules see page 9/6 SITOP selectivity modules see page 9/14 Stabilized power supply Input: 400 ... 500 V 3 AC Output: 24 V DC/20 A SITOP buffer modules see page 9/16 SITOP DC UPS see page 8/2 SITOP PSU8200 3-phase, 24 V DC/40 A 6EP3437-8SB00-0AY0 Device identification label 3RT2900-1SB20 Stabilized power supply Input: 400 ... 500 V 3 AC Output: 24 V DC/20 A

# Advanced power supplies

SITOP PSU8200

### Overview



The 3-phase SITOP modular are technology power supplies for sophisticated solutions and offer maximum functionality for use in complex plants and machines. The wide-range input allows connection to almost any electrical power system worldwide and ensures a high degree of safety, even if there are large voltage fluctuations. The power boost provides up to three times the rated current for brief periods. In case of overload, you can choose between constant current with automatic restart or latching shutdown. The high degree of efficiency keeps energy consumption and heating in the control cabinet low, and the compact metal housing also saves space.

#### Main product highlights

- 36 V DC/13 A
- 3-phase AC input 400 to 500 volts
- Extremely slim design no lateral installation clearances required
- Power boost with 3 times the rated current (for 25 ms) for tripping protective devices
- Extra power with 1.5 times the rated current (5 s/min) for brief functional overload
- Choice of constant current or latching shutdown short-circuit response
- Optional symmetrical load distribution for parallel operation
- Operating state on 3 LEDs
- Extremely high efficiency up to 94%
- Wide temperature range from -25 to +70 °C
- Comprehensive certifications, such as cULus, ATEX

#### Technical specifications

·	
Article number	6EP3446-8SB10-0AY0
Product	SITOP PSU8200
Power supply, type	36 V/13 A
Input	0 share AO
Input Rated voltage value V	3-phase AC 400 500 V
Rated voltage value V <sub>in rated</sub> Voltage range AC	320 575 V
Wide-range input	Yes
Mains buffering at $I_{out rated}$ , min.	15 ms; at V <sub>in</sub> = 400 V
Rated line frequency 1	50 Hz
Rated line frequency 2	60 Hz
Rated line range	47 63 Hz
Input current	
<ul> <li>at rated input voltage 400 V</li> </ul>	1.2 A
at rated input voltage 500 V	1 A
Switch-on current limiting (+25 °C), max.	16 A
l²t, max.	0.8 A <sup>2.</sup> s
Built-in incoming fuse	none
Protection in the mains power input	Required: 3-pole connected
(IEC 898)	miniature circuit breaker 6 16 A characteristic C or circuit breaker
	3RV2011-1DA10 (setting 3 A) or
<u></u>	3RV2711-1DD10 (UL 489)
Output Output	Controlled, isolated DC voltage
Rated voltage $V_{out rated}$ DC	36 V
Total tolerance, static $\pm$	3 %
Static mains compensation, approx.	0.1 %
Static load balancing, approx.	0.2 %
Residual ripple peak-peak, max.	100 mV
Spikes peak-peak, max.	200 mV
(bandwidth: 20 MHz)	36 42 V
Adjustment range Product function Output voltage	Yes
adjustable	
Output voltage setting	via potentiometer; max. 480 W
Status display	Green LED for 36 V OK
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for 36 V OK
On/off behavior	No overshoot of $V_{out}$ (soft start)
Startup delay, max.	2.5 s
Voltage increase time of the output	500 ms
voltage maximum	
Rated current value <i>I</i> <sub>out rated</sub>	13 A
Current range  • Note	0 13 A
Supplied active power typical	+60 +70 °C: Derating 2%/K 468 W
Short-term overload current	
<ul> <li>at short-circuit during operation</li> </ul>	39 A
typical	
Duration of overloading capability for excess current	
<ul> <li>at short-circuit during operation</li> </ul>	25 ms
Constant overload current	
• on short-circuiting during the start- up typical	14 A
Parallel switching for enhanced performance	Yes; switchable characteristic
Numbers of parallel switchable units for enhanced performance	2

3-phase, 36 V DC

Article number	6EP3446-8SB10-0AY0	Article I
Product	SITOP PSU8200	Product
Power supply, type	36 V/13 A	Power s
Efficiency		Operatir
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	94 %	Ambient <ul> <li>during</li> </ul>
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	30 W	- Note
Closed-loop control		<ul> <li>during</li> </ul>
Dynamic mains compensation ( <i>V<sub>in rated</sub> ±</i> 15 %), max.	0.1 %	during     Humidity     FNLCOZC
Dynamic load smoothing ( $I_{out}$ : 50/100/50 %), $U_{out} \pm typ$ .	1 %	EN 6072 Mechan
Load step setting time 50 to 100%, typ.	0.2 ms	Connect Connect
Load step setting time 100 to 50%, typ.	0.2 ms	<ul> <li>Supply</li> </ul>
Dynamic load smoothing ( <i>I</i> <sub>out</sub> : 10/90/10 %), <i>U</i> <sub>out</sub> ± typ.	2 %	<ul> <li>Outpu</li> </ul>
Load step setting time 10 to 90%, typ.	0.2 ms	·
Load step setting time 90 to 10%, typ.	0.2 ms	<ul> <li>Auxilia</li> </ul>
Setting time maximum	10 ms	
Protection and monitoring		
Output overvoltage protection	< 48 V	Width of
Current limitation, typ.	14 A	Height c
Property of the output Short-circuit proof	Yes	Depth o Require
Short-circuit protection	Alternatively, constant current characteristic approx. 14 A or latching shutdown	<ul><li>top</li><li>botton</li></ul>
Enduring short circuit current RMS value		<ul><li>left</li><li>right</li></ul>
typical	14 A	Weight,
Overcurrent overload capability in normal operation	overload capability 150 % / <sub>out rated</sub> up to 5 s/min	Product housing
Overload/short-circuit indicator	LED yellow for "overload", LED red for "latching shutdown"	Installati
Safety		Mechan
Primary/secondary isolation	Yes	
Galvanic isolation	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Other in
Protection class	Class I	
Leakage current		
• maximum	3.5 mA	Orderi
• typical		
CE mark	Yes	SITOP P
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1,	36 V DC
Explosion protection	UL 60950-1) IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc;	Input: 3 Output: 3
	cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4	Access
FM approval	-	SITOP re
CB approval	Yes	RED120
Marine approval	-	Device i
Degree of protection (EN 60529)	IP20	
EMC		
Emitted interference	EN 55022 Class B	
Supply harmonics limitation	EN 61000-3-2	
· · · ·	EN 61000-6-2	

Article number	6EP3446-8SB10-0AY0	
Product	SITOP PSU8200	
Power supply, type	36 V/13 A	
Operating data		
Ambient temperature		
during operation	-25 +70 °C	
- Note	with natural convection	
during transport	-40 +85 °C	
during storage	-40 +85 °C	
Humidity class according to EN 60721	Climate class 3K3, no condensation	
Mechanics		
Connection technology	screw-type terminals	
Connections		
Supply input	L1, L2, L3, PE: 1 screw terminal each for 0.2 4 mm <sup>2</sup> single-core/finely stranded	
Output	+, -: 2 screw terminals each for 0.2 4 mm <sup>2</sup>	
• Auxiliary	13, 14 (alarm signal): 1 screw terminal each for 0.14 1.5 mm <sup>2</sup> ; 15, 16 (Remote): 1 screw terminal each for 0.14 1.5 mm <sup>2</sup>	
Width of the enclosure	70 mm	
Height of the enclosure	125 mm	
Depth of the enclosure	125 mm	
Required spacing		
• top	50 mm	
bottom	50 mm	
• left	0 mm	
• right	0 mm	
Weight, approx.	1.2 kg	
Product feature of the enclosure housing for side-by-side mounting	Yes	
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	
Mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	
Ordering data	Article No.	
SITOP PSU8200 3-phase, 36 V DC/13 A	6EP3446-8SB10-0AY0	
Stabilized power supply Input: 3 400 500 V AC Output: 36 V DC/13 A		
Accessories	Article No.	
SITOP redundancy modules RED1200	see page 9/6	
Device identification labels	3RT2900-1SB20	

## Advanced power supplies

SITOP PSU8200

#### Overview



3-phase SITOP modular devices are technology power supplies for sophisticated solutions and offer maximum functionality for use in complex plants and machines. The wide-range input allows a connection to almost any electrical power system worldwide and ensures a high degree of safety even if there are large voltage fluctuations. The power boost provides up to three times the rated current for brief periods. In case of overload, you can choose between constant current with automatic restart or latching shutdown. The high degree of efficiency keeps energy consumption and heating in the control cabinet low, and the compact metal housing also saves space.

#### Main product highlights

- 48 V DC / 10 A and 20 A
- 3-phase wide-range input
- Extremely slim design no lateral installation clearances required
- Power Boost with 3 times the rated current (for 25 ms) for tripping protective devices
- Extra power with 1.5 times the rated current (5 s/min) for brief functional overload
- Selectable short-circuit response between constant current and restart
- Optional symmetrical load distribution for parallel operation
- Operating status on 3 LEDs
- Extremely high efficiency up to 95%
- Wide temperature range from -25 to +70 °C
- Comprehensive certifications, such as cULus, ATEX and DNV GL

Article number	6EP3446-8SB00-0AY0	6EP3447-8SB00-0AY0
Product	SITOP PSU8200	SITOP PSU8200
Power supply, type	48 V/10 A	48 V/20 A
Input		
Input	3-phase AC	3-phase AC
Rated voltage value Vin rated	400 500 V	400 500 V
Voltage range AC	320 575 V	320 575 V
Wide-range input	Yes	Yes
Mains buffering at Iout rated, min.	15 ms; at V <sub>in</sub> = 400 V	10 ms; at $V_{in} = 400 \text{ V}$
Rated line frequency 1	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz
Rated line range	47 63 Hz	45 65 Hz
Input current		
<ul> <li>at rated input voltage 400 V</li> </ul>	1.2 A	2 A
<ul> <li>at rated input voltage 500 V</li> </ul>	1 A	1.7 A
Switch-on current limiting (+25 °C), max.	16 A	13 A
l²t, max.	0.8 A <sup>2</sup> ·s	2.24 A <sup>2</sup> ·s
Built-in incoming fuse	none	-
Protection in the mains power input (IEC 898)	Required: 3-pole connected miniature circuit breaker 6 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)	Required: 3-pole connected miniature circuit breaker 10 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)
Output		
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage V <sub>out rated</sub> DC	48 V	48 V
Total tolerance, static $\pm$	3 %	3 %
Static mains compensation, approx.	0.1 %	0.1 %
Static load balancing, approx.	0.2 %	0.2 %
Residual ripple peak-peak, max.	100 mV	100 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV	480 mV
Adjustment range	42 56 V	46 56 V
Product function Output voltage adjustable	Yes	Yes
Output voltage setting	via potentiometer; max. 480 W	via potentiometer; max. 960 W
Status display	Green LED for 48 V OK	Green LED for 48 V OK

#### Technical specifications

2

Article number	6EP3446-8SB00-0AY0	6EP3447-8SB00-0AY0
Product	SITOP PSU8200	SITOP PSU8200
Power supply, type	48 V/10 A	48 V/20 A
Output (continued)		
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for 48 V OK	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for 48 V OK
On/off behavior	No overshoot of Vout (soft start)	minimal overshoot (< 3 %)
Startup delay, max.	2.5 s	0.1 s
Voltage increase time of the output voltage maximum	500 ms	100 ms
Rated current value Iout rated	10 A	20 A
Current range	0 10 A	0 20 A
Note	+60 +70 °C: Derating 2%/K	+60 +70 °C: Derating 4%/K
Supplied active power typical	480 W	960 W
Short-term overload current	aa 4	aa 4
at short-circuit during operation typ.	30 A	60 A
Duration of overloading capability for excess current		
at short-circuit during operation	25 ms	25 ms
Constant overload current	11 A	04.4
• on short-circuiting during the start- up typical	11 A	24 A
Parallel switching for enhanced performance	Yes; switchable characteristic	Yes; switchable characteristic
Numbers of parallel switchable units for enhanced performance	2	2
Efficiency		
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	94 %	94 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	31 W	58 W
Power loss [W] during no-load operation maximum	-	4 W
Closed-loop control	0.1.0%	
Dynamic mains compensation $(V_{\text{in rated }\pm15 \text{ \%}})$ , max.	0.1 %	1%
Dynamic load smoothing ( $I_{out}$ : 50/100/50 %), $U_{out} \pm$ typ.	1%	3 %
Load step setting time 50 to 100%, typ.	0.2 ms	-
Load step setting time 100 to 50%, typ.	0.2 ms	-
Dynamic load smoothing ( <i>I</i> <sub>out</sub> : 10/90/10 %), <i>U</i> <sub>out</sub> ± typ.	2 %	-
Load step setting time 10 to 90%, typ.		-
Load step setting time 90 to 10%, typ.		-
Setting time maximum	10 ms	10 ms
Protection and monitoring		57.0.1/
Output overvoltage protection	< 60 V	< 57.8 V
Current limitation, typ.	11 A	22 A
Property of the output Short-circuit proof Short-circuit protection	Alternatively, constant current characteristic approx. 11 A	Yes Alternatively, constant current characteristic approx. 22 A
Enduring short circuit current RMS val.		or latching shutdown
• typical	11 A	26 A
Overcurrent overload capability in normal operation	overload capability 150 % Iout rated up to 5 s/min	overload capability 150 % <i>I</i> <sub>out rated</sub> up to 5 s/min
Overload/short-circuit indicator	LED yellow for "overload", LED red for "latching shutdown"	LED yellow for "overload", LED red for "latching shutdown"
Safety		
Primary/secondary isolation	Yes	Yes
Galvanic isolation	Safety extra low output voltage $V_{\rm out}$ according to EN 60950-1	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178
Protection class	Class I	Class I
Leakage current		
• maximum	3.5 mA	1 mA
• typical	0.9 mA	0.6 mA
CE mark	Yes	Yes

# Advanced power supplies SITOP PSU8200

# 3-phase, 48 V DC

Article number	6EP3446-8SB00-0AY0		6EP3447-8SB00-0A	YO
Product	SITOP PSU8200		SITOP PSU8200	
Power supply, type	48 V/10 A		48 V/20 A	
Safety (continued)				
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No E197259; cCSAus (CSA C22.2 No. 60			08, CSA C22.2 No. 107.1), File CSA C22.2 No. 60950-1, UL 60950-
Explosion protection	IECEX EX NA NC IIC T4 Gc; ATEX (EX) T4; cCSAus (CSA C22.2 No. 213, AN) Class I, Div. 2, Group ABCD, T4			T4 Gc; ATEX (EX) II 3G Ex nA nC IIC 22.2 No. 213, ANSI/ISA-12.12.01) p ABCD, T4
FM approval	-		-	
CB approval	Yes		Yes	
Marine approval	ABS, DNV GL		-	
Degree of protection (EN 60529)	IP20		IP20	
EMC				
Emitted interference	EN 55022 Class B		EN 55022 Class B	
Supply harmonics limitation	EN 61000-3-2		EN 61000-3-2	
Noise immunity	EN 61000-6-2		EN 61000-6-2	
Operating data				
Ambient temperature				
<ul> <li>during operation</li> </ul>	-25 +70 °C		-25 +70 °C	
- Note	with natural convection		With natural convect	tion
<ul> <li>during transport</li> </ul>	-40 +85 °C		-40 +85 °C	
during storage	-40 +85 °C		-40 +85 °C	
Humidity class according to EN 60721	Climate class 3K3, no condensation			no condensation
Mechanics				
Connection technology	screw-type terminals		screw-type terminals	3
Connections				
Supply input			L1, L2, L3, PE: 1 scr single-core/finely str	rew terminal each for 0.5 4 mm <sup>2</sup> randed
Output	+, -: 2 screw terminals each for 0.2 4 mm <sup>2</sup>		+: 2 screw terminals terminals each for 0	each for 0.5 16 mm <sup>2</sup> ; -: 3 screw .5 16 mm <sup>2</sup>
Auxiliary	0.14 1.5 mm <sup>2</sup> ;	13, 14 (alarm signal): 1 screw terminal each for		), screw terminal each for 0.05 2.5
Width of the enclosure	70 mm		135 mm	
Height of the enclosure	125 mm			
Depth of the enclosure	125 mm		150 mm	
Required spacing				
• top	50 mm		40 mm	
bottom	50 mm		40 mm	
• left	0 mm		0 mm	
• right	0 mm		0 mm	
Weight, approx.	1.2 kg		3.3 kg	
Product feature of the enclosure housing for side-by-side mounting	Yes		Yes	
Installation	Snaps onto DIN rail EN 60715 35x7.5	/15	Snaps onto DIN rail	EN 60715 35x15
Mechanical accessories	Device identification label 20 mm × 7 mm, Tl-grey 3RT2900-1SB20		Device identification 3RT2900-1SB20	label 20 mm × 7 mm, TI-grey
MTBF at 40 °C			520 782 h	
Other information	Specifications at rated input voltage a temperature +25 °C (unless otherwise			ed input voltage and ambient (unless otherwise specified)
Ordering data	Article No.	Accessories		Article No.
3-phase SITOP PSU8200, 48 V DC/10 A	6EP3446-8SB00-0AY0	SITOP modular For 6EP1XXX-3B	signaling module	6EP1961-3BA10
			/ 100	

3-phase SITOP PSU8200, 48 V DC/10 A	6EP3446-8SB00-0AY0	SITOP modular signaling module For 6EP1XXX-3BA00	6EP1961-3BA10
Stabilized power supply Input: 3 AC 400 500 V Output: 48 V DC/10 A		Signaling contacts: Output voltage OK, operating readiness OK,	
SITOP PSU8200, 3-phase, 48 V DC/20 A	6EP3447-8SB00-0AY0	remote ON/OFF SITOP PSU1200 redundancy	see page 9/6
Stabilized power supply		modules	
Input: 3 AC 400 500 V Output: 48 V DC/20 A		Device identification labels	3RT2900-1SB20

© Siemens 2019

# Standard power supplies



3/2	Introduction
<b>3/3</b>	SITOP PSU6200
3/3	Introduction
3/4	1-phase, 12 V DC
3/8	1-phase, 24 V DC
<b>3/15</b>	SITOP smart
3/15	Introduction
3/16	1-phase, 12 V DC
3/19	1-phase, 24 V DC
3/24	3-phase, 24 V DC

Introduction		
1-phase, 12 V DC		
1-phase, 24 V DC		
3-phase 24 V DC		

## Standard power supplies

### Introduction

#### Overview

Our standard portfolio has been designed with typical industrial requirements in mind, such as those in series machine production.

The versatile new SITOP PSU6200 was developed on the basis of our experience with the time-proven SITOP smart product line. This new SITOP Standard offers even more efficiency, extensive diagnostic options and enhanced robustness.

#### Introduction

#### Overview



SITOP PSU6200 family

# High performance – Focused diagnostics – The all-round power supply for a wide variety of applications

The SITOP PSU6200 product family is the new standard power supply for customers with extreme technical requirements regarding reliability, efficiency and integration. It is suitable for many fields of application, particularly in the industrial environment, such as series machine building. The SITOP PSU6200 represents the state-of-the-art and takes the SITOP product portfolio into new dimensions of efficiency.

The stabilized 1-phase power supplies with a wide input range of 120–230 V AC nominal voltage and 120–240 V DC are available with an output voltage of 12 V in three performance classes and with an output voltage of 24 V in six performance classes. The premium design of the PSU6200 series, in connection with the push-in terminals, represents effective wiring. The modules in this product family are all-rounders featuring a long service life and absolute reliability.

The high level of efficiency across the entire load range, as well as the minimal no-load losses, result in lower overall energy consumption. New levels of convenience during commissioning and service are offered for modules of 10 A or more by the diagnostic monitor with LED indicators for DC o.k., utilization and service life, as well as the diagnostics interface for reporting status information. For power supplies with an output of more than 10 A, the DC o.k. status is also equipped with glitch recognition that indicates even the smallest supply voltage failures.

For power supply modules up to 10 A, a diagnostics LED indicates DC o.k.; this information is also reported by means of a relay for devices of 3.7 A and above.

To further increase the 24 V availability, the SITOP PSU6200 power supplies can be combined with **buffer**, **DC UPS**, **redundancy** and **selectivity modules**.

#### Main product highlights

- Diagnostic monitor from 10 A output power
   LED display for DC o.k., utilization and operating hours
- · Diagnostics interface from 10 A output power
  - Provision of important operating parameters (e.g. power, voltage, overload, etc.)
- · Constant current
  - Up to 15 V supply voltage for 24 V devices, up to 9 V supply voltage for 12 V devices
  - Power supply not switched off immediately in the event of overload
- Robust AC input
- Active PFC
- Optimized protection of the input circuit
- DC capability / wide-range input
- Enhanced versatility and reliability
- Coordinated product family
- Comprehensive range of products for a wide range of requirements
- Narrow overall width
  - For direct side-by-side mounting without lateral clearance requirements
  - Attractive metal enclosures from 3.7 A, plastic enclosure up to 2.5 A with similar form and color
- Push-in terminals
  - Easy, time-saving installation without need for tools
  - Separate ground terminal
- · Selectivity and redundancy modules
  - Narrow width
  - In SITOP PSU6200 design

#### Standard power supplies

SITOP PSU6200

#### Overview



SITOP PSU6200 family 12 V

#### High performance - Focused diagnostics - The all-round power supply for a wide variety of applications

The SITOP PSU6200 product family is the new standard power supply for customers with extreme technical requirements regarding reliability, efficiency and integration. It is suitable for many fields of application, particularly in the industrial environment, such as series machine building. The SITOP PSU6200 represents the state-of-the-art and takes the prized SITOP design to new dimensions of efficiency.

The stabilized 1-phase power supplies with a wide input range of 120-230 V AC nominal voltage and 120-240 V DC are available with an output voltage of 12 V in three performance classes and with an output voltage of 24 V in six performance classes.

The premium design of the PSU6200 series, in connection with the push-in terminals, represents effective wiring. The modules in this product family are all-rounders featuring a long service life and absolute reliability.

The high level of efficiency across the entire load range, as well as the minimal no-load losses, result in lower overall energy consumption. New levels of convenience during commissioning and service are offered for modules of 10 A or more by the diagnostic monitor with LED indicators for DC o.k., utilization and service life, as well as the diagnostics interface for reporting status information. For power supplies with an output of more than 10 A, the DC o.k. status is also equipped with glitch recognition that indicates even the smallest supply voltage failures.

For power supply modules up to 10 A, a diagnostics LED indicates DC o.k.; this information is also reported by means of a relay for devices of 3.7 A and above.

#### Main product highlights

- Diagnostic monitor from 10 A output performance - LED display for DC o.k., utilization and operating hours
- Diagnostics interface from 10 A output performance Provision of important operating parameters (e.g. power, voltage, overload, etc.)
- Constant current
- Up to 15 V supply voltage for 24 V devices, up to 9 V supply voltage for 12 V devices
- Power supply not switched off immediately in the event of overload
- Robust AC input
- Active PFC
- Optimized protection of the input circuit
- DC capability / wide-range input
- Enhanced versatility and reliability
- Coordinated product family
- Comprehensive range of products for a wide range of requirements
- Narrow overall width
- For direct side-by-side mounting without lateral clearance requirements
- Attractive metal enclosures from 3.7 A, plastic enclosure up to 2.5 A with similar form and color
- Push-in terminals
  - Easy, time-saving installation without need for tools
  - Separate ground terminal
- Redundancy modules
- Narrow width
- In SITOP PSU6200 design

# Technical specifications

Article number Product	6EP3321-7SB00-0AX0 <sup>1)</sup> SITOP PSU6200	6EP3323-7SB00-0AX0 <sup>1)</sup> SITOP PSU6200	6EP3324-7SB00-3AX0 <sup>1)</sup> SITOP PSU6200
Power supply, type	12 V/2 A	12 V/7 A	12 V/12 A
Input	12 112 12		
Input	1-phase AC or DC	1-phase AC or DC	1-phase AC or DC
Rated voltage value V <sub>in rated</sub>	120 230 V	120 230 V	120 230 V
Voltage range AC	85 264 V	85 264 V	85 264 V
Supply voltage		00 20	00 20 1 1
• at DC	120 240 V	120 240 V	110 240 V
Input voltage			
• at DC	110 275 V	99 275 V	85 275 V
Wide-range input	Yes	Yes	Yes
Overvoltage resistance	300 V AC for 30 s	300 V AC for 30 s	300 V AC for 30 s
Mains buffering at I <sub>out rated</sub> , min.	150 ms; at V <sub>in</sub> = 230 V	90 ms; at $V_{in} = 230$ V	70 ms; at $V_{in} = 230$ V
Rated line frequency 1	50 Hz	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz	47 63 Hz
Input current	17 00 112	11 00 112	
at rated input voltage 120 V	0.45 A	1.4 A	1.4 A
<ul> <li>at rated input voltage 230 V</li> </ul>	0.25 A	0.8 A	0.8 A
Switch-on current limiting (+25 °C),	32 A	29 A	6 A
max.	0277	2077	
Built-in incoming fuse	3.15 A	3.15 A	5 A
Output			
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Number of outputs	1	1	1
Rated voltage Vout rated DC	12 V	12 V	12 V
Total tolerance, static $\pm$	3 %	3 %	3 %
Static mains compensation, approx.	0.3 %	0.1 %	0.1 %
Static load balancing, approx.	0.3 %	0.2 %	0.1 %
Residual ripple peak-peak, max.	30 mV	30 mV	30 mV
Residual ripple peak-peak, typ.	20 mV	20 mV	20 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	20 mV	100 mV	30 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	10 mV	60 mV	20 mV
Adjustment range	10.5 12.9 V	12 15.5 V	12 15.5 V
Product function Output voltage adjustable	Yes	Yes	Yes
Output voltage setting	via potentiometer; max. 24 W	via potentiometer; max. 84 W (100 W up to 45°C)	via potentiometer; max. 144 W (173 W up to 45°C)
Status display	Green LED for 24 V OK	Green LED for 24 V OK	Green LED for 24 V OK
Signaling		Electronic contact (NO contact, contact rating 60 V DC/0.1 A) for 24 V O.K. or diagnostic interface	Electronic contact (NO contact, contact rating 60 V DC/0.1 A) for 24 V O.K. or diagnostic interface
On/off behavior	Overshoot of Vout approx. 3 %	Overshoot of $V_{out} < 2 \%$	Overshoot of $V_{out} < 2 \%$
Startup delay, max.	1s	0.5 s	0.5 s
Voltage rise, typ.	50 ms	100 ms	100 ms
Rated current value Iout rated	2 A	7 A	12 A
Current range	0 2 A	0 7 A	0 12 A
Note	+60 +70 °C: Derating 2%/K	8.4 A up to +45°C; +60 +70 °C: Derating 2%/K	14.4 A up to +45°C; +60 +70 °C: Derating 2%/K

# Standard power supplies SITOP PSU6200

# 1-phase, 12 V DC

## Technical specifications (continued)

Article number	6EP3321-7SB00-0AX0 <sup>1)</sup>	6EP3323-7SB00-0AX0 <sup>1)</sup>	6EP3324-7SB00-3AX0 <sup>1)</sup>
Product	SITOP PSU6200	SITOP PSU6200	SITOP PSU6200
Power supply, type	12 V/2 A	12 V/7 A	12 V/12 A
Output (continued)			
Supplied active power typical	24 W	84 W	144 W
Short-term overload current			
<ul> <li>on short-circuiting during the start- up typical</li> </ul>	2 A	8.4 A	14.4 A
<ul> <li>at short-circuit during operation typical</li> </ul>	2 A	8.4 A	14.4 A
Product feature parallel switching of outputs	-	-	can be set with DIP switch
Parallel switching for enhanced performance	-	-	switchable characteristic
Numbers of parallel switchable units for enhanced performance			2
Efficiency			
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	83.3 %	86.6 %	89.3 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	5 W	13 W	17 W
Power loss [W] during no-load operation maximum	0.8 W	1.8 W	3 W
Closed-loop control			
Dynamic load smoothing ( <i>I</i> <sub>out</sub> : 10/90/10 %), <i>U</i> <sub>out</sub> ± typ.	4 %	3 %	3 %
Load step setting time 10 to 90%, typ.	2 ms	1 ms	2 ms
Load step setting time 90 to 10%, typ.	2 ms	1 ms	2 ms
Setting time maximum	3 ms	2 ms	3 ms
Protection and monitoring			
Output overvoltage protection	< 20 V	< 20 V	< 20 Vu
Current limitation, typ.	2.8 A	8.4 A	14.4 A
Property of the output Short-circuit proof	Yes	Yes	Yes
Short-circuit protection	Shutdown and periodic restart attempts	Shutdown and periodic restart attempts	Shutdown and periodic restart attempts
Overcurrent overload capability in normal operation	-	overload capability 150 % <i>I</i> <sub>out rated</sub> up to 5 s/min	overload capability 150 % <i>l</i> <sub>out rated</sub> up to 5 s/min
Safety			
Primary/secondary isolation	Yes	Yes	Yes
Galvanic isolation	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Safety extra low output voltage $V_{out}$ according to EN 60950-1
Protection class	Class I	Class I	Class I
Leakage current			
• maximum	3.5 mA	3.5 mA	3.5 mA
CE mark	Yes	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
Explosion protection	-	-	-
FM approval	-	-	-
CB approval	Yes	Yes	Yes
Regulatory Compliance Mark (RCM)	No	No	No
Marine approval	in process: DNV GL, ABS	in process: DNV GL, ABS	in process: DNV GL, ABS
Degree of protection (EN 60529)	IP20	IP20	IP20
EMC			
Emitted interference	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2	EN 61000-3-2	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2

Article number	6EP3321-7SB00-0AX01)	6EP3323-7SB00-0AX0 <sup>1)</sup>	6EP3324-7SB00-3AX0 <sup>1)</sup>
Product	SITOP PSU6200	SITOP PSU6200	SITOP PSU6200
Power supply, type	12 V/2 A	12 V/7 A	12 V/12 A
Operating data			
Ambient temperature			
<ul> <li>during operation</li> </ul>	-25 +70 °C	-25 +70 °C	-25 +70 °C
- Note	with natural convection	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensatio
Mechanics			
Connection technology	Push-in terminals	Push-in terminals	Push-in terminals
Connections			
Supply input	L1/+, L2/N/-; PE PushIn for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	L1/+, L2/N/-; PE PushIn for 0.5 4 mm <sup>2</sup> single-core/finely stranded	L1/+, L2/N/-; PE PushIn for 0.5 4 mm <sup>2</sup> single-core/finely stranded
• Output	+1, -1, -2: PushIn for 0.5 2.5 mm <sup>2</sup>	+1, +2, -1, -2, -3: PushIn for 0.5 2.5 mm <sup>2</sup>	+1, +2, -1, -2, -3: PushIn for 0.5 2.5 mm <sup>2</sup>
Auxiliary	-	13, 14 (alarm signal): 1 push-in terminal each for 0.2 1.5 mm <sup>2</sup>	13, 14 (alarm signal): 1 push-in terminal each for 0.2 1.5 mm <sup>2</sup>
Width of the enclosure	25 mm	35 mm	45 mm
Height of the enclosure	100 mm	135 mm	135 mm
Depth of the enclosure	88 mm	125 mm	125 mm
Required spacing			
• top	50 mm	45 mm	45 mm
bottom	50 mm	45 mm	45 mm
• left	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
Electrical accessories	Redundancy module	Redundancy module	Redundancy module
Mechanical accessories	SIMATIC ET 200SP equipment labels: 6ES7193-6LF30-0AW0	SIMATIC ET 200SP equipment labels: 6ES7193-6LF30-0AW0	SIMATIC ET 200SP equipment labe 6ES7193-6LF30-0AW0

1) Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Ordering data	Article No.	Accessories	Article No.
SITOP PSU6200 1-phase, 12 V DC/2 A	6EP3321-7SB00-0AX0	SITOP RED1200 redundancy module	6EP4346-7RB00-0AX0
Stabilized power supply Input: 120–230 V AC/120–240 V DC Output: 12 V DC/2 A		Input/output: 12 V DC, 24 V, 48 V/20 A (maximum total current) Suitable for decoupling two SITOP	
SITOP PSU6200 1-phase, 12 V DC/7 A	6EP3323-7SB00-0AX0	power supplies with a maximum of 10 A output current each	
Stabilized power supply Input: 120–230 V AC/120–240 V DC		SITOP RED1200 redundancy module	6EP4347-7RB00-0AX0
Output: 12 V DC/7 A SITOP PSU6200 1-phase, 12 V DC/12 A	6EP3324-7SB00-3AX0	Input/output: 12 V DC, 24 V, 48 V/40 A (maximum total current) Suitable for decoupling two SITOP power supplies with a maximum of	
Stabilized power supply Input: 120–230 V AC/110–240 V DC Output: 12 V DC/12 A		20 A output current each SIMATIC ET 200SP labels	6ES7193-6LF30-0AW0
		160 equipment labeling plates, 10 sheets (160 plates)	

#### More information

Select the appropriate power supply quickly and easily with the TIA Selection Tool: http://www.siemens.com/tst

### Standard power supplies

SITOP PSU6200

#### Overview



SITOP PSU6200 family 24 V

#### High performance - Focused diagnostics - The all-round power supply for a wide variety of applications

The SITOP PSU6200 product family is the new standard power supply for customers with extreme technical requirements regarding reliability, efficiency and integration. It is suitable for many fields of application, particularly in the industrial environment, such as series machine building. The SITOP PSU6200 represents the state-of-the-art and takes the prized SITOP design to new dimensions of efficiency.

The stabilized 1-phase power supplies with a wide input range of 120-230 V AC nominal voltage and 120-240 V DC are available with an output voltage of 12 V in three performance classes and with an output voltage of 24 V in six performance classes.

The premium design of the PSU6200 series, in connection with the push-in terminals, represents effective wiring. The modules in this product family are all-rounders featuring a long service life and absolute reliability.

The high level of efficiency across the entire load range, as well as the minimal no-load losses, result in lower overall energy consumption. New levels of convenience during commissioning and service are offered for modules of 10 A or more by the diagnostic monitor with LED indicators for DC o.k., utilization and service life, as well as the diagnostics interface for reporting status information. For power supplies with an output of more than 10 A, the DC o.k. status is also equipped with glitch recognition that indicates even the smallest supply voltage failures.

For power supply modules up to 10 A, a diagnostics LED indicates DC o.k.; this information is also reported by means of a relay for devices of 3.7 A and above.

#### Main product highlights

- Diagnostic monitor from 10 A output performance - LED display for DC o.k., utilization and operating hours
- Diagnostics interface from 10 A output performance - Provision of important operating parameters (e.g. power, voltage, overload, etc.)
- · Constant current
  - Up to 15 V supply voltage for 24 V devices, up to 9 V supply voltage for 12 V devices
  - Power supply not switched off immediately in the event of overload
- Robust AC input
- Active PFC
- Optimized protection of the input circuit
- DC capability / wide-range input
- Enhanced versatility and reliability
- Coordinated product family
- Comprehensive range of products for a wide range of requirements
- Narrow overall width
- For direct side-by-side mounting without lateral clearance requirements
- Attractive metal enclosures from 3.7 A, plastic enclosure up to 2.5 A with similar form and color
- Push-in terminals
  - Easy, time-saving installation without need for tools
  - Separate ground terminal
- · Selectivity and redundancy modules
  - Narrow width
  - In SITOP PSU6200 design

# Technical specifications

Partice function         Personal resolution         Personal resolution         Personal resolution         Personal resolution           Product         STOP PSUE200         <	Article number	6EP3331-7SB00-0AX0 <sup>1)</sup>	6EP3332-7SB00-0AX0 <sup>1)</sup>	6EP3333-7LB00-0AX0 <sup>1)</sup>
Process papely, type         24 V/3 A         24 V/2 S A         24 V/3 A           Input         - I-phase AC or DC         1 -phase AC or DC         1 -phase AC or DC           Bated voltage value V <sub>1 tables</sub> 120 20 V         120 20 V         120 20 V           Supply voltage         -         -         -         -           at DC         120 240 V         120 240 V         120 240 V           in DC         120 240 V         120 240 V         120 240 V           in DC         10 275 V         120 240 V         120 240 V           in DC         100 275 V         09 275 V         09 275 V           Voltage range input         Yes         Yes         Yes         000 VAC for 30 s           At DC Devotage residence         300 VAC for 30 s         300 VAC for 30 s         000 VAC for 30 s           At Devotage residence         300 VAC for 30 s         01 Hz         01 Hz         01 Hz           At Devotage residence         300 VAC for 30 s         01 Hz         01 Hz         01 Hz           At Devotage residence         300 VAC for 30 s         01 Hz         01 Hz         01 Hz           At Devotage residence         300 VAC for 30 s         01 Hz         01 Hz	Article number			
IpputIpputIppase AC or DCIppase AC or DCFailed voltage value $V_{in tabel}$ 120230 V120230 V120230 VVoltage range AC85264 V85264 V85264 V• at DC120230 V120240 V120240 V• at DC120275 V120275 V99275 V• at DC110275 V110275 V99275 V• at DC110275 V110275 V99275 V• at DC110275 V110275 V90 mm; at $V_{p} = 230 V$ • at DC1150 mm; at $V_{p} = 230 V$ 90 mm; at $V_{p} = 230 V$ • at at dia flag the flag under this50 Hz50 Hz• at at add inda the flag under this50 Hz50 Hz• at at add inda the flag at add this150 ms; at $V_{p} = 230 V$ • at add inda the flag under this0.8 A1.1 A1.5 A• at attach ing the flag at 20 V0.6 A1.1 A1.5 A• at attach ing the flag at 20 V0.6 A3.5 A2.5 A• at attach ing the flag at 20 V3.6 A3.15 A3.15 A• at attach ing the flag at 20 V3.6 A3.5 A2.5 A• at attach ing the flag at 20 V3.6 A3.5 A3.5 A• at attach ing the flag at 20 V3.6 A3.5 A3.5 A• at attach ing the flag at 20 V3.6 A3.5 A3.5 A• at attach ing the flag at 20 V3.6 A3.5 A3.5 A• at attach ing the flag at 20 V3.6 A3.5 A3.5 A• at attach ing the flag a				
Input         Inplase AC or DC         Inplase AC or DC         Inplase AC or DC           Relate village variage AC         85 264 V         85 264 V         85 264 V           Supply voltage         120 230 V         120 230 V         120 230 V           supply voltage         120 240 V         120 240 V         120 240 V           is DC         110 275 V         99 275 V         99 275 V           Voltage range input         Yes         300 VAC for 30 S         300 VAC for 30 S           Voltage range input         Yes         Yes         90 275 V           Voltage range input         Yes         300 VAC for 30 S         300 VAC for 30 S           Attack line frequency 1         150 rs, at Y <sub>n</sub> = 230 V         50 Hz         60 Hz           Attack line frequency 1         50 Hz         60 Hz         60 Hz         60 Hz           Attack dinput voltage 120 V         0.6 A         0.6 A         0.5 A         32 A           Statistic number of trans the intergeneron         31 FA         31 FA         31 FA           Output         Controlled, isolated DC voltage         Controlled, isolated DC voltage         11 FA           Attack data pack data 2         3 %         3 %         3 %         3 %         <		24 V/1.3 A	24 V/2.3 A	24 V/3./ A
Finance voltage value V <sub>r result</sub> 120230 V         120230 V         120230 V           Supply voltage         -         -         -         -           - at DC         120240 V         -         -         -         -           - at DC         120240 V         -	•	1-phase AC or DC	1-phase AC or DC	1-phase AC or DC
Voltage range AC         85 264 V         85 264 V         85 264 V           Supply voltage	•			
Supp Input outge at DC         Input outge 120201V         Input outge 120201V         Input outge 120201V           • at DC         110275 V         110275 V         120201V           • at DC         110275 V         120201V         90275 V           • at DC         120201V         120201V         90275 V           • Vas         Vas         Vas         90275 V           • Vas         00.VAC for 30 s         300 VAC for 30 s         300 ms, 21 V <sub>0</sub> - 230 V           • Attack Inter factors of Log tasks         50 Hz         50 Hz         50 Hz           • Attack Inter factors of Log tasks         60 Hz         60 Hz         60 Hz           • Attack Inter voltage 120 V         0.6 A         1.1 A         1.5 A           • Attack Input voltage 120 V         0.6 A         1.1 A         1.5 A           • Attack Input voltage 120 V         0.6 A         3.15 A         3.15 A           • Attack Input voltage 120 V         0.6 A         3.15 A         3.15 A           • Attack Input voltage 120 V         3.15 A         3.15 A         3.15 A           • Attack Input voltage 120 V         3.15 A         3.15 A         3.15 A           • Attack Input voltage 120 V         3.15 A         3.15 A         3.15				
• al DC         120 240 V         120 240 V         120 240 V           Input votage         110 275 V         110 275 V         99 275 V           • al DC         110 275 V         110 275 V         99 275 V           Wole-range input         Ves         Ves         Ves         Ves           Overvotage resistance         300 VAC for 30 s           All als for input on the status of the status		05 204 V	00 204 V	00 204 V
Input voltage         Imput voltage resistance         Imput voltage resistance         Imput voltage resistance           Vervoltage resistance         300 V AC for 30 s         300 V AC for 30 s         300 V AC for 30 s           Mans buffering at V <sub>operator</sub> (M = 230 V         50 Hz         50 Hz         50 Hz           Read inte frequency 1         60 Hz         60 Hz         60 Hz           Read inte frequency 2         60 Hz         60 Hz         60 Hz           Read inte frequency 2         60 Hz         60 Hz         60 Hz           Input current         -         4763 Hz         15 A           - a trade input voltage 230 V         0.3 A         0.6 A         0.6 A           - a trade input voltage 230 V         0.3 A         0.6 A         0.6 A           Switch-on current limiting (42 Hz), (2, C), (3, ZA         3.15 A         3.15 A           Poter         -         Controlled, isolated DC voltage         Con	,	120 240 1/	120 240 1/	120 240 \/
• at D         10 $275 \vee$ 10 $275 \vee$ 99 $275 \vee$ Wide-range input         Yes         Yes         Yes         Yes         Yes         Yes         Yes           Outwortlage resistance         300 V AC for 30 s		120 240 V	120 240 V	120 240 V
Wide-range inputYesYesYesYesOvervoltage resistance300 V for 30 s300 V AC for 30 s300 V AC for 30 sMains buffengi d_bartage/150 ms; at $V_{\mu} = 230$ V50 Hz50 HzBade line frequency 160 Hz60 Hz60 HzBade line range47 63 Hz47 63 Hz47 63 HzPiput currentPiput currentSwitch-on current limiting (+25 °C), max.35 AOutputOutputOutputOutputOutputOutputOutputNumbar of outputs1-1Read voltage peak-peak, max30 mV-3%Static boot balancing, approx0.1%0.1%0.0 mVStatic back balancing, approx0.1%0.0 mVStatic back balancing, approx0.1%0.0 mVStatic back balancing, approx0.0 mV <td></td> <td>110 275 \/</td> <td>110 075 1/</td> <td>00 275 \/</td>		110 275 \/	110 075 1/	00 275 \/
Overvoltage resistance         300 V AC for 30 s           Mains bullering at log ranged min.         150 ms; at $V_{\mu} = 230 V$ 50 Hz         50 Hz         50 Hz           Rated line frequency 1         50 Hz         60 Hz         60 Hz         60 Hz         60 Hz           Rated line frequency 2         60 Hz         60 Hz         60 Hz         60 Hz         60 Hz           rated input voltage 120 V         0.6 A         1.1 A         1.5 A         7.6 Hz           ot at rated input voltage 210 V         0.6 A         3.7 A         32A         32A           Bulth in incoming fuse         3.15 A         3.5 A         3.5 A         3.5 A           Output         Controlled, isolated DC voltage         Controlled, isolated DC voltage         Controlled, isolated DC voltage           Output         Controlled, isolated DC voltage         Controlled, isolated DC voltage         Controlled, isolated DC voltage           Static mains compensation, approx         0.1%         0.1%         0.3 %         S         S           Static mains compensation, approx         0.1%         0.1 %         0.3 %         S         S           Static mains compensation, approx         0.1 %         0.1 %         0				
Mains bulkering at $l_{0.41 attach min.}$ 150 ms; at $V_{a1} = 230$ V         90 ms; at $V_{a1} = 230$ V           Rated in frequency 1         50 Hz         50 Hz         60 Hz           Rated in frequency 2         60 Hz         60 Hz         60 Hz           rated in frequency 2         60 Hz         4763 Hz         4763 Hz           input current         -         -         -         -           - at rated input voltage 230 V         0.3 A         0.6 A         0.9 A           Switch-on current limiting (+25 °C), max.         315 A         315 A         315 A           Output         Controlled, isolated DC voltage         Controlled, isolated DC voltage         Controlled, isolated DC voltage           Output         Controlled, isolated DC voltage         1         1         1           Rated voltage V <sub>041</sub> man DC         24 V         24 V         24 V           Static nains compensation, approx.         0.1 %         0.1 %         0.3 %           Static nains compensation, approx.         0.1 %         0.1 %         0.3 %           Static nains compensation, approx.         0.1 %         0.1 %         0.3 %           Static nains compensation, approx.         0.1 %         0.1 %         0.3 %           Static nad balancing, approx.<	• ·			
Rated line frequency 1S0 HzS0 HzS0 HzS0 HzS0 HzS0 HzRated line frequency 260 Hz60 Hz60 Hz60 Hz60 HzRated line range4763 Hz4763 Hz763 Hz763 HzInput current at rated input voltage 120 V0.6 A1.1 A1.5 A- at rated input voltage 220 V0.3 A0.6 A0.9 ASwitch-on current limiting (+25 °C), rax.32 A316 A3.16 AOutputControlled, isolated DC voltageControlled, isolated DC voltageControlled, isolated DC voltageNumber of outputs1111Rated voltage V <sub>0,171800</sub> DC24 V24 V24 VStatic nairs compensation, approx.0.1 %0.1 %0.3 %Static nairs compensation, approx.0.1 %0.1 %0.3 %Static nairs compensation, approx.0.1 %0.0 mV30 mVSplet peak-peak, rinz.30 mV30 mV30 mV00 mVSplet peak-peak, rinz.30 mV20 mV20 mV20 mVSplet peak-peak, rinz.20 mV20 mV20 mV20 mVSplet peak-peak, rinz.30 mV30 mV00 mVSplet peak-peak, rinz.30 mV20 mV20 mVSplet peak-peak, rinz.30 mV<	•			
Hated line frequency 2         60 Hz         60 Hz         60 Hz           Rated line range         4763 Hz         4763 Hz         4763 Hz           Pated line range         4763 Hz         4763 Hz         4763 Hz           Pated line range         100 Hz         11.4         15.A           I rated input voltage 230 V         0.5 A         0.6 A         0.9 A           Switch-on current limiting (+25 °C), max.         32 A         29 A           Bullt-in incoming fuse         3.15 A         3.15 A           Dutput         Controlled, isolated DC voltage         Controlled, isolated DC voltage           Number of outputs         1         1         1           Rated voltage V <sub>uin rated</sub> DC         24 V         24 V         24 V           Static load balancing, approx.         0.1 %         0.1 %         0.3 %           Static load balancing, approx.         0.1 %         0.1 %         0.3 %           Static load balancing, approx.         0.1 %         0.1 %         0.0 %           Static load balancing, approx.         0.1 %         0.0 mV         0.0 mV           Chard Width: 20 MH2)         30 mV         0.0 mV         0.0 mV           Static load balancing, approx.         30 mV         0.0 mV <td></td> <td></td> <td></td> <td></td>				
Hated line range         4763 Hz         4763 Hz         4763 Hz           Input current				
Input currentControlled, isolated DCControlled, isolated DCSecond Controlled, isolated DC $\bullet$ at rated input voltage 230 V0.3 A32 A32 ASwitch-on current limiting (+25 °C), max.32 A32 A32 ABuilt-in incoming fuse3.15 A3.15 A3.15 AOutputControlled, isolated DC voltageControlled, isolated DC voltageControlled, isolated DC voltageNumber of outputs111Rated voltage Voltage DC24 V24 VValiation and ancing, approx.0.1 %0.1 %0.2 %Static load balancing, approx.0.1 %0.1 %0.3 %Static load balancing, approx.0.1 %0.1 %0.3 mVResidual rippic peak-peak, max.30 mV30 mV30 mVSpikes peak-peak, max.30 mV30 mV20 mVSpikes peak-peak, max.30 mV30 mV00 mVAdjustment range22.2				
• at rated input voltage 120 V0.6 A1.1 A1.5 A• at rated input voltage 230 V0.3 A0.6 A0.9 ASwitch-on current limiting (+25 °C), max.32 A32 A29 ADutputControlled, isolated DC voltage3.15 A3.15 AOutputControlled, isolated DC voltageControlled, isolated DC voltageControlled, isolated DC voltageNumber of outputs111Rated voltage V <sub>out rated</sub> DC24 V24 V24 VTotal tolerance, static $\pm$ 3 %3 %3 %Static mains compensation, approx.0.1 %0.1 %0.2 %Static peak-peak, max.30 mV30 mV30 mVSpikes peak-peak, max.30 mV30 mV20 mVSpikes peak-peak, max.30 mV20 mV20 mVSpikes peak-peak, max.30 mV22 26 4 V24 28 VProduct function Output voltage adjustablevia potentiometer, max. 31.2 Wvia potentiometer, max. 60 Wvia potentiometer, max. 89 W (106 W up to 45°C)Statu displayGreen LED for 24 V OKGreen LED for 24 V OKGreen LED for 24 V OKGreen LED for 24 V OKSignaling1 s1 s1 s0 37 AOutput delay, max.1 s1 s0 37 AOutput delay in the	e e e e e e e e e e e e e e e e e e e	47 03 HZ	47 03 HZ	47 03 Π2
• at rated input voltage 230 V Switch-on current limiting ( $\pm 25  ^{\circ}$ ), fax.0.3 A 32 A0.6 A 32 A0.9 A 32 ASwitch-on current limiting ( $\pm 25  ^{\circ}$ ), rax.32 A32 A29 ABull-in incoming fuse3.15 A3.15 A3.15 AOutputControlled, isolated DC voltage 1Number of outputs1111111Rated voltage Voltage do tarbuts3%3%3%Static mains compensation, approx.0.1 %0.1 %0.2 %Static load balancing, approx.0.1 %0.1 %0.3 %Residual ripple peak-peak, max.30 mV30 mV30 mVSpikes peak-peak, max.30 mV30 mV00 mVSpikes peak-peak, max.30 mV20 mV00 mVSpikes peak-peak, max.30 mV20 mV00 mVSpikes peak-peak, max.30 mV20 mV00 mVSpikes peak-peak, tp.22264 V2428 VProduct function Output voltage adjustableVesYesOutput voltage settingvia potentiometer; max. 31.2 Wvia potentiometer; max. 60 WSpinalingCreen LED for 24 V OKGreen LED for 24 V OKSpinalingSo ms1 s1 sOutput voltage setting1.3 A2.5 A3.7 ASharup delay, max.013 A2.5 A3.7 ASharup delay, max.1.3 A2.5 A3.7 ASharup delay max.1.3 A2.5 A3.7 ASharup d		0.0.4	1 1 A	1 5 4
Switch-on current limiting (+25 °C), max.32 A32 A29 ADutty3.15 A3.15 A3.15 AOutputControlled, isolated DC voltageControlled, isolated DC voltageControlled, isolated DC voltageNumber of outputs111Rated voltage V <sub>out</sub> rated DC24 V24 V24 VStatic mains compensation, approx.0.1 %0.1 %0.2 %Static icad balancing, approx.0.1 %0.1 %0.3 %Static bad balancing, approx.0.1 %0.1 %0.3 %Residual ripple peak-peak, max.30 mV30 mV20 mVSpikes peak-peak, max.30 mV20 mV20 mVSpikes peak-peak, reak, max.30 mV20 mV20 mVSpikes peak-peak, typ.20 mV30				
max.SiteSiteSiteBuilt-in inoring fuseS.15 AS.15 AS.15 AOutputControlled, isolated DC voltageControlled, isolated DC voltageControlled, isolated DC voltageNumber of outputs11SiteFated voltage $V_{out}$ rated DC24 V24 VValues $V_{out}$ rated DC3%3%3%Static isolated balancing, approx.0.1%0.1%0.2%Static isolated balancing, approx.0.1%0.1%0.3%Residual ripple peak-peak, max.30 mV30 mV30 mVResidual ripple peak-peak, max.30 mV20 mV20 mVSpikes peak-peak, max.30 mV20 mV00 mVSpikes peak-peak, max.30 mV20 mV60 mVAdjustment range22 $\dots$ 26.4 V24 $\dots$ 28 VProduct function Output voltage adjustablevia potentiometer; max. 31.2 Wvia potentiometer; max. 60 WOutput voltage settingvia potentiometer; max. 31.2 Wvia potentiometer; max. 60 Wvia potentiometer; max. 89 WSignalingOutput voltage setting50 ms1s55 sSoltau displayGreen LED for 24 V OKGreen LED for 24 V OKGreen LED for 24 V OKFeen LED for 24 V OKSignalingOutput voltage fies, typ.50 ms1s55 sVoltage rise, typ.50 ms100 ms0.37 A </td <td></td> <td></td> <td></td> <td></td>				
Output         Controlled, isolated DC voltage         Controlled, isolated DC voltage         Controlled, isolated DC voltage           Number of outputs         1         1         1         1         1           Rated voltage V <sub>out rated</sub> DC         24 V         24 V         24 V         24 V           Total tolerance, statio ±         3 %         3 %         3 %         3 %         3 %           Static ical balancing, approx.         0.1 %         0.1 %         0.3 %         0.2 %           Static load balancing, approx.         0.1 %         0.1 %         0.3 %           Pesidual ripple peak-peak, max.         30 mV         30 mV         30 mV         30 mV           Spikes peak-peak, typ.         20 mV         20 mV         20 mV         60 mV           (bandwidth: 20 MHz)         30 mV         30 mV         22 26.4 V         24 28 V           Yes         Yes         Yes         Yes         Yes         Yes           Output voltage setting         via potentiometer; max. 31.2 W         via potentiometer; max. 60 W         via potentiometer; max. 89 W         (106 W up to 45°C)           Status display         Green LED for 24 V OK         Green LED for 24 V OK         Green LED for 24 V OK         Contact rating 60 V D(C) 1.1 h) for 24 V OK <tr< td=""><td></td><td>32 A</td><td>32 A</td><td>29 A</td></tr<>		32 A	32 A	29 A
OutputControlled, isolated DC voltageControlled, isolated DC voltageControlled, isolated DC voltageNumber of outputs111Rated voltage $V_{out}$ nated DC24 V24 VOtal tolerance, static $\pm$ 3%3%3%Static mains compensation, approx.0.1 %0.1 %0.2 %Static load balancing, approx.0.1 %0.1 %0.3 %Residual ripple peak-peak, max.30 mV30 mV30 mVSpikes peak-peak, max.30 mV30 mV20 mVSpikes peak-peak, nax.30 mV20 mV00 mVSpikes peak-peak, typ.20 mV20 mV20 mV/<	Built-in incoming fuse	3.15 A	3.15 A	3.15 A
Number of outputs111Rated voltage $V_{out rated}$ DC24 V24 V24 VTotal tolerance, static $\pm$ 3%3%3%Total tolerance, static $\pm$ 3%3%3%Static mains compensation, approx.0.1%0.1%0.2%Static bad balancing, approx.0.1%0.1%0.3%Residual ripple peak-peak, max.30 mV20 mV20 mVSpikes peak-peak, max.30 mV20 mV20 mVSpikes peak-peak, max.30 mV20 mV00 mVSpikes peak-peak, max.30 mV20 mV60 mVSpikes peak-peak, max.20 mV20 mV60 mVSpikes peak-peak, max.22.226.4 V2428 VProduct function Output voltage adjustable22.226.4 V2428 VOutput voltage settingvia potentiometer; max. 31.2 Wvia potentiometer; max. 60 Wvia potentiometer; max. 89 W (106 W up to 45°C)Statu displayGreen LED for 24 V OKGreen LED for 24 V OKGreen LED for 24 V OKSignalingOn/off behaviorOvershoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> < 2 %Statup delay, max.111	Output			
Rated voltage Volt rated DC24 V24 V24 VTotal tolerance, static ±3 %3 %3 %Static mains compensation, approx.0.1 %0.1 %0.2 %Static ad balancing, approx.0.1 %0.1 %0.3 %Residual ripple peak-peak, max.30 mV30 mV30 mVResidual ripple peak-peak, max.30 mV20 mV20 mVSpikes peak, peak, max.30 mV20 mV00 mVSpikes peak, peak, max.30 mV20 mV60 mVSpikes peak, peak, typ.20 mV20 mV40 mV(bandwidth: 20 MHz)20 mV22 26.4 V24 28 VProduct function Output voltage adjustableYesYesYesOutput voltage settingvia potentiometer; max. 31.2 Wvia potentiometer; max. 60 Wvia potentiometer; max. 89 W (106 W up to 45°C)Status displayGreen LED for 24 V OKGreen LED for 24 V OKEffectionic contact (NO contact, contact rating 60 V DC/0.1 A) for 24 V O.K. or diagnostic interfaceOrlof behaviorOvershoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Status display50 ms100 ms100 msRated current value ( <sub>out</sub> rated to unit approx.1.82.5 A3.7 AVoltage rise, typ.0 13A2.5 A3.7 ANote+60 +70 °C: Derating 2.5%/K+60 +70 °C: Derating 1.5%/K9.0 MShort-term overload current u pipolal1.3 A2.5 A3.7 A• Note+60 +70 °C: Derat	Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Total tolerance, static $\pm$ 3 %3 %3 %3 %Static mains compensation, approx.0.1 %0.1 %0.2 %Static load balancing, approx.0.1 %0.1 %0.3 %Residual ripple peak-peak, max.30 mV30 mV30 mVResidual ripple peak-peak, typ.20 mV20 mV20 mVSpikes peak-peak, max.30 mV20 mV60 mVSpikes peak-peak, typ.20 mV20 mV60 mVSpikes peak-peak, typ.20 mV22 26.4 V24 28 VProduct function Output voltage adjustableYesYesYesOutput voltage settingvia potentiometer; max. 31.2 Wvia potentiometer; max. 60 Wvia potentiometer; max. 89 WSignalingGreen LED for 24 V OKGreen LED for 24 V OKGreen LED for 24 V OKElectronic contact (NO contact, contact rating 60 V DC/0.1 A) for 24 V OK.SignalingNo1.3 A1.5 NA0 2.5 A3.7 AVoltage rise, typ.0 1.3 A0 2.5 A0 3.7 ANote+0 +70 °C: Derating 2.5%/K+60 +70 °C: Derating 1.5%/K89 WShort-erroving during the start- up typical1.3 A2.5 A3.7 A	Number of outputs	1	1	1
Static mains compensation, approx. $0.1\%$ $0.1\%$ $0.1\%$ $0.2\%$ Static load balancing, approx. $0.1\%$ $0.1\%$ $0.3\%$ Residual ripple peak-peak, max. $30 \text{ mV}$ $30 \text{ mV}$ $30 \text{ mV}$ Residual ripple peak-peak, max. $30 \text{ mV}$ $20 \text{ mV}$ $20 \text{ mV}$ Spikes peak-peak, typ. $30 \text{ mV}$ $20 \text{ mV}$ $20 \text{ mV}$ Spikes peak-peak, typ. $20 \text{ mV}$ $20 \text{ mV}$ $60 \text{ mV}$ (bandwidth: $20 \text{ MHz})$ $20 \text{ mV}$ $20 \text{ mV}$ $60 \text{ mV}$ Spikes peak-peak, typ. $20 \text{ mV}$ $22 \dots 26.4 \text{ V}$ $24 \dots 28 \text{ V}$ (bandwidth: $20 \text{ MHz})$ $22 \dots 26.4 \text{ V}$ $22 \dots 26.4 \text{ V}$ $24 \dots 28 \text{ V}$ Spikes peak-peak, typ. $100 \text{ mV}$ $100 \text{ mV}$ $100 \text{ mV}$ (bandwidth: $20 \text{ MHz})$ $20 \text{ mV}$ $20 \text{ mV}$ $20 \text{ mV}$ Spikes peak-peak, typ. $100 \text{ mV}$ $20 \text{ mV}$ $24 \dots 28 \text{ V}$ (bandwidth: $20 \text{ MHz})$ $22 \dots 26.4 \text{ V}$ $24 \dots 28 \text{ V}$ Spikes peak-peak, typ. $100 \text{ mV}$ $100 \text{ mV}$ Adjustent range $22 \dots 26.4 \text{ V}$ $22 \dots 26.4 \text{ V}$ $24 \dots 28 \text{ V}$ Product function obupt voltage $100 \text{ mV}$ $100 \text{ mV}$ $100 \text{ mV}$ Spipe peak-peak, typ. $100 \text{ peak}$ $100 \text{ peak}$ $100 \text{ mV}$ Status displayGreen LED for $24 \text{ VOK}$ Green LED for $24 \text{ VOK}$ Green LED for $24 \text{ VOK}$ Signaling $1 \text{ S}$ $1 \text{ S}$ $0 \text{ Overshoot of V_{out}} approx. 3\%$ $0  Voershoot of V_{o$	Rated voltage Vout rated DC	24 V	24 V	24 V
Static load balancing, approx. $0.1\%$ $0.1\%$ $0.1\%$ $0.3\%$ Residual ripple peak-peak, max. $30 \text{ mV}$ $30 \text{ mV}$ $30 \text{ mV}$ $30 \text{ mV}$ Residual ripple peak-peak, max. $30 \text{ mV}$ $20 \text{ mV}$ $20 \text{ mV}$ $20 \text{ mV}$ Spikes peak-peak, max. $30 \text{ mV}$ $30 \text{ mV}$ $00 \text{ mV}$ (bandwidth: $20 \text{ MHz}$ ) $20 \text{ mV}$ $20 \text{ mV}$ $60 \text{ mV}$ Spikes peak-peak, typ. $20 \text{ mV}$ $20 \text{ mV}$ $60 \text{ mV}$ (bandwidth: $20 \text{ MHz}$ ) $20 \text{ mV}$ $20 \text{ mV}$ $24 \dots 28 \text{ V}$ Adjustment range $22.2 \dots 26.4 \text{ V}$ $22.2 \dots 26.4 \text{ V}$ $24 \dots 28 \text{ V}$ Product function Output voltage adjustablevia potentiometer; max. $31.2 \text{ W}$ via potentiometer; max. $89 \text{ W}$ ( $106 \text{ Wup to 45\%)Output voltage settingvia potentiometer; max. 31.2 \text{ W}via potentiometer; max. 89 \text{ W}(106 \text{ Wup to 45\%)Status displayGreen LED for 24 \text{ V OK}Green LED for 24 \text{ V OK}Electronic contact (NO contact,contact rating 60 \text{ VDC}). 1 \text{ A} for24 \text{ V O.K or diagnostic interfaceOn/off behaviorOvershoot of V_{out} approx. 3\%Overshoot of V_{out} approx. 3\%Overshoot of V_{out} < 2\%Status displaySo ms100 \text{ ms}30 \text{ ms}100 \text{ ms}Rated current value I_{out rated}1.3 \text{ A}2.5 \text{ A}3.7 \text{ A}Note40 \dots, 170 ^{\circ}: Derating 2.5\%/K40 \dots, 170 ^{\circ}: Derating 1.5\%/K89 \text{ W}Short-term overload current1.3 \text{ A}2.5 $	Total tolerance, static $\pm$	3 %	3 %	3 %
Residual ripple peak-peak, max. Residual ripple peak-peak, max. (bandwidth: 20 MH2)30 mV30 mV20 mVSpikes peak-peak, max. (bandwidth: 20 MH2)30 mV30 mV100 mVSpikes peak-peak, typ. (bandwidth: 20 MH2)20 mV20 mV60 mVAdjustment range22.226.4 V22.226.4 V2428 VProduct function Output voltage adjustableYesYesYesOutput voltage settingvia potentiometer; max. 31.2 Wvia potentiometer; max. 60 Wvia potentiometer; max. 89 W (106 W up to 45°C)Status displayGreen LED for 24 V OKGreen LED for 24 V OKGreen LED for 24 V OKSignalingOn/off behaviorOvershoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Status display50 ms100 ms100 ms0.5 sStatus display1.3 A2.5 A3.7 AOn/off behavior0 1.3 A0 2.5 A 3.7 ANote400 +70 °C: Derating 1.5%/K80 WSupplied active power typical Supplied active power typical1.3 A2.5 A3.7 ANote1.3 A2.5 A3.7 ASupplied active power typical a typical1.3 A2.5 A3.7 AAugust and the typical supplical1.3 A3.5 A3.7 AAugust and the typical a typical1.3 A3.5 A3.7 AAugust and the typical a typical1.3 A3.5 A3.7 AAugust and typical a typical1.3 A	Static mains compensation, approx.	0.1 %	0.1 %	0.2 %
Residual ripple peak-peak, typ. Spikes peak-peak, max. (bandwidth: 20 MHz)20 mV20 mV20 mVSpikes peak-peak, typ. (bandwidth: 20 MHz)20 mV20 mV60 mVAdjustment range22.2 26.4 V22.2 26.4 V24 28 VProduct function Output voltage adjustableYesYesYesOutput voltage settingvia potentiometer; max. 31.2 Wvia potentiometer; max. 60 Wvia potentiometer; max. 89 W (106 W up to 45°C)Status displayGreen LED for 24 V OKGreen LED for 24 V OKGreen LED for 24 V OKSignalingElectronic contact (NO contact, contact rating 60 V DC/0.1 A) for 24 V O.K. or diagnostic interfaceOn/off behaviorOvershoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Voltage rise, typ.50 ms100 ms 3.7 ARated current value I <sub>out rated</sub> 1.3 A0 2.5 A 3.7 ASupplied active power typical31.2 W60 W89 WShort-term overload current 1.3 A2.5 A 3.7 ASupplied active power typical1.3 A2.5 A 3.7 ASupplied active power typical1.3 A2.5 A 3.7 AShort-term overload current 1.3 A 2.5 A 3.7 ASupplied active power typical1.3 A 2.5 A 3.7 ASupplied active power typical1.3 A 2.5 A 3.7 ASupplied active power typical1.3 A 2.5 A 3.7 ASupplied acti	Static load balancing, approx.	0.1 %	0.1 %	0.3 %
Spikes peak-peak, max. (bandwidth: 20 MHz)30 mV30 mV100 mVSpikes peak-peak, typ. (bandwidth: 20 MHz)20 mV20 mV60 mVAdjustment range22 26 4 V22 26 4 V24 28 VProduct function Output voltage adjustableYesYesYesOutput voltage settingvia potentiometer; max. 31.2 Wvia potentiometer; max. 60 Wvia potentiometer; max. 89 W (106 W up to 45°C)Status displayGreen LED for 24 V OKGreen LED for 24 V OKGreen LED for 24 V OKSignalingElectronic contact (NO contact, contact rating 60 V DC/0.1 A) for 24 V O.K. or diagnostic interfaceOn/off behaviorOvershoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Voltage rise, typ.50 ms100 ms100 msRated current value l <sub>out rated</sub> 1.3 A2.5 A3.7 ASupplied active power typical31.2 W60 W89 WShort-term overload current1.3 A2.5 A3.7 A• on short-circuiting during the start- up typical1.3 A2.5 A3.7 A• at short-circuit during operation1.3 A2.5 A3.7 A	Residual ripple peak-peak, max.	30 mV	30 mV	30 mV
(bandwidth: 20 MHz)ComVComVComVSpikes peak-peak, typ. (bandwidth: 20 MHz)20 mV20 mV20 mV20 mVAdjustment range22.2 26.4 V22.2 26.4 V24 28 VProduct function Output voltage adjustableYesYesYesOutput voltage settingvia potentiometer; max. 31.2 Wvia potentiometer; max. 60 Wvia potentiometer; max. 89 W (106 W up to 45°C)Status displayGreen LED for 24 V OKGreen LED for 24 V OKGreen LED for 24 V OKSignalingOn/off behaviorOvershoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Statup delay, max.1 s1 s0.0 ms3.7 AVoltage rise, typ.0 1.3 A0 2.5 A 3.7 ANote+60 +70 °C: Derating 2.5%/K+60 +70 °C: Derating 1.5%/K99 WSupplied active power typical1.3 A2.5 A3.7 Aon short-circuiting during the start up typical1.3 A2.5 A3.7 Aon short-circuit during operation1.3 A2.5 A3.7 A	Residual ripple peak-peak, typ.	20 mV	20 mV	20 mV
(bandwidth: 20 MHz)22.2 26.4 V22.2 26.4 V24 28 VAdjustment range22.2 26.4 V22.2 26.4 V24 28 VProduct function Output voltage adjustableYesYesYesOutput voltage settingvia potentiometer; max. 31.2 Wvia potentiometer; max. 60 Wvia potentiometer; max. 89 W (106 W up to 45°C)Status displayGreen LED for 24 V OKGreen LED for 24 V OKGreen LED for 24 V OKSignalingOn/off behaviorOvershoot of Vout approx. 3 %Overshoot of Vout approx. 3 %Overshoot of Vout approx. 3 %Statup delay, max.1 s1 s0.5 sVoltage rise, typ.50 ms100 ms3.7 ARated current value lout rated1.3 A2.5 A0 3.7 AOn/oft behavior9 1.3 A60 W89 WSupplied active power typical31.2 W60 W89 WShort-terro userlad current1.3 A2.5 A3.7 AOn short-circuiting during the start1.3 A2.5 A3.7 ASupplied active power typical31.2 W60 W89 WShort-terro userlad current1.3 A2.5 A3.7 ASupplied active power typical1.3 A3.5 A3.7 ASupplied active power typical1.3 A3.5 A3.7 ASupplied active power typical1.3 A3.5 A3.7 ASupplied active power typical3.1 A3.5 A3.7 ASupplied active power typical1.3 A3.5 A3.7 A <t< td=""><td></td><td>30 mV</td><td>30 mV</td><td>100 mV</td></t<>		30 mV	30 mV	100 mV
Product function Output voltage adjustableYesYesYesOutput voltage settingvia potentiometer; max. 31.2 Wvia potentiometer; max. 60 Wvia potentiometer; max. 89 WOutput voltage settingvia potentiometer; max. 31.2 Wvia potentiometer; max. 60 Wvia potentiometer; max. 89 WStatus displayGreen LED for 24 V OKGreen LED for 24 V OKGreen LED for 24 V OKSignalingElectronic contact (NO contact, contact rating 60 V DC/0.1 A) for 24 V O.K. or diagnostic interfaceOn/off behaviorOvershoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Startup delay, max.1 s1 s0.5 sVoltage rise, typ.50 ms100 ms0.0 msRated current value I <sub>out rated</sub> 1.3 A2.5 A3.7 AOutput applied active power typical31.2 W60 W89 WShort-term overload current1.3 A2.5 A3.7 A• on short-circuiting during the start pup typical1.3 A2.5 A3.7 A• on short-circuit during operation1.3 A3.5 A3.7 A		20 mV	20 mV	60 mV
adjustablevia potentiometer; max. 31.2 Wvia potentiometer; max. 60 Wvia potentiometer; max. 89 W (106 W up to 45°C)Status displayGreen LED for 24 V OKGreen LED for 24 V OKGreen LED for 24 V OKSignaling	Adjustment range	22.2 26.4 V	22.2 26.4 V	24 28 V
Status displayGreen LED for 24 V OKGreen LED for 24 V OKGreen LED for 24 V OKSignalingElectronic contact (NO contact, contact rating 60 V DC/0.1 A) for 24 V O.K. or diagnostic interfaceOn/off behaviorOvershoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %On/off behaviorOvershoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %On/off behaviorOvershoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Overshoot of V <sub>out</sub> approx. 3 %Startup delay, max.1 s1 s0.5 sVoltage rise, typ.50 ms100 ms100 msRated current value I <sub>out rated</sub> 1.3 A2.5 A3.7 ACurrent range0		Yes	Yes	Yes
Signaling- Another Signaling	Output voltage setting	via potentiometer; max. 31.2 W	via potentiometer; max. 60 W	
On/off behaviorOvershoot of $V_{out}$ approx. 3 %Overshoot of $V_{out} < 2$ %Startup delay, max.1 s1 s0.5 s0.5 sVoltage rise, typ.50 ms100 ms100 ms100 msRated current value $I_{out rated}$ 1.3 A2.5 A3.7 ACurrent range0 1.3 A0 2.5 A0 3.7 A• Note+60 +70 °C: Derating 2.5%/K+60 +70 °C: Derating 1.5%/K89 WShort-term overload current• on short-circuiting during the starture1.3 A2.5 A3.7 A• at short-circuit during operation1.3 A2.5 A3.7 A	Status display	Green LED for 24 V OK	Green LED for 24 V OK	Green LED for 24 V OK
Startup delay, max.1 s0.5 sVoltage rise, typ.50 ms100 ms100 msRated current value lout rated1.3 A2.5 A3.7 ACurrent range01.3 A02.5 A03.7 A• Note+60+70 °C: Derating 2.5%/K+60+70 °C: Derating 1.5%/K89 WSupplied active power typical31.2 W60 W89 WShort-term overload current• on short-circuiting during the startur up typical1.3 A2.5 A3.7 A• at short-circuit during operation1.3 A2.5 A3.7 A	Signaling	-	-	contact rating 60 V DC/0.1 A) for
Voltage rise, typ.50 ms100 ms100 msRated current value lout rated1.3 A2.5 A3.7 ACurrent range01.3 A02.5 A03.7 A• Note+60+70 °C: Derating 2.5%/K+60+70 °C: Derating 1.5%/K89 WSupplied active power typical31.2 W60 W89 WShort-term overload current3.7 A• on short-circuiting during the start1.3 A2.5 A3.7 A• at short-circuit during operation1.3 A2.5 A3.7 A	On/off behavior	Overshoot of Vout approx. 3 %	Overshoot of Vout approx. 3 %	Overshoot of $V_{out} < 2 \%$
Rated current value $l_{out rated}$ 1.3 A2.5 A3.7 ACurrent range01.3 A02.5 A03.7 A• Note+60+70 °C: Derating 2.5%/K+60+70 °C: Derating 1.5%/K89 W• Supplied active power typical31.2 W60 W89 WShort-term overload current	Startup delay, max.	1 s	1 s	0.5 s
Current range01.3 A02.5 A03.7 A• Note+60+70 °C: Derating 2.5%/K+60+70 °C: Derating 1.5%/K89 WSupplied active power typical31.2 W60 W89 WShort-term overload current3.7 A• on short-circuiting during the start up typical1.3 A2.5 A3.7 A	Voltage rise, typ.	50 ms	100 ms	100 ms
• Note+60 +70 °C: Derating 2.5%/K+60 +70 °C: Derating 1.5%/K89 WSupplied active power typical31.2 W60 W89 WShort-term overload current• on short-circuiting during the start up typical1.3 A2.5 A3.7 A• at short-circuit during operation1.3 A2.5 A3.7 A	Rated current value <i>I</i> out rated	1.3 A	2.5 A	3.7 A
Supplied active power typical31.2 W60 W89 WShort-term overload current• on short-circuiting during the start- up typical1.3 A2.5 A3.7 A• at short-circuit during operation1.3 A2.5 A3.7 A	Current range	0 1.3 A	0 2.5 A	0 3.7 A
Short-term overload currentImage: Short-term overload current• on short-circuiting during the start- up typical1.3 A2.5 A3.7 A• at short-circuit during operation1.3 A2.5 A3.7 A	Note	+60 +70 °C: Derating 2.5%/K	+60 +70 °C: Derating 1.5%/K	
Short-term overload currentImage: Short-term overload current• on short-circuiting during the start- up typical1.3 A2.5 A3.7 A• at short-circuit during operation1.3 A2.5 A3.7 A	Supplied active power typical	31.2 W	60 W	89 W
up typical     • at short-circuit during operation     1.3 A     2.5 A     3.7 A				
		1.3 A	2.5 A	3.7 A
		1.3 A	2.5 A	3.7 A

6EP3332-7SB00-0AX01)

6EP3333-7LB00-0AX01)

# Standard power supplies

**Technical specifications** (continued)

SITOP PSU6200

# 1-phase, 24 V DC

Article number	6EP3331-7SB00-0AX01)
Product	SITOP PSU6200
Power supply, type	24 V/1.3 A
Efficiency	
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	86.3 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	5 W
Power loss [W] during no-load operation maximum	0.8 W
Closed-loop control	
Dynamic load smoothing ( <i>I</i> <sub>out</sub> : 10/90/10 %), <i>U</i> <sub>out</sub> ± typ.	2 %
Load step setting time 10 to 90%, typ.	0.5 ms
	0 5

Product	SITOP PSU6200	SITOP PSU6200	SITOP PSU6200
Power supply, type	24 V/1.3 A	24 V/2.5 A	24 V/3.7 A
Efficiency			
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	86.3 %	89 %	89.3 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	5 W	7 W	11 W
Power loss [W] during no-load operation maximum	0.8 W	0.8 W	2.2 W
Closed-loop control			
Dynamic load smoothing ( <i>I</i> <sub>out</sub> : 10/90/10 %), <i>U</i> <sub>out</sub> ± typ.	2 %	3 %	2 %
Load step setting time 10 to 90%, typ.	0.5 ms	1 ms	2 ms
Load step setting time 90 to 10%, typ.	0.5 ms	1 ms	2 ms
Setting time maximum	1 ms	2 ms	3 ms
Protection and monitoring			
Output overvoltage protection	< 32 V	< 32 V	< 32 V
Current limitation, typ.	1.6 A	3.1 A	3.7 A
Property of the output Short-circuit proof	Yes	Yes	Yes
Short-circuit protection	Shutdown and periodic restart attempts	Shutdown and periodic restart attempts	Shutdown and periodic restart attempts
Safety			
Primary/secondary isolation	Yes	Yes	Yes
Galvanic isolation	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1
Protection class	Class I	Class I	Class I
Leakage current			
• maximum	3.5 mA	3.5 mA	3.5 mA
CE mark	Yes	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
Explosion protection	-	-	-
FM approval	-	-	-
CB approval	Yes	Yes	Yes
Regulatory Compliance Mark (RCM)	No	No	No
Marine approval	in process: DNV GL, ABS	in process: DNV GL, ABS	in process: DNV GL, ABS
Degree of protection (EN 60529)	IP20	IP20	IP20
EMC			
Emitted interference	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2	EN 61000-3-2	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data			
Ambient temperature			
<ul> <li>during operation</li> </ul>	-25 +70 °C	-25 +70 °C	-25 +70 °C
- Note	with natural convection	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C
during storage	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation

Article number	6EP3331-7SB00-0AX0 <sup>1)</sup>	6EP3332-7SB00-0AX01)	6EP3333-7LB00-0AX0 <sup>1)</sup>
Product	SITOP PSU6200	SITOP PSU6200	SITOP PSU6200
Power supply, type	24 V/1.3 A	24 V/2.5 A	24 V/3.7 A
lechanics			
Connection technology	Push-in terminals	Push-in terminals	Push-in terminals
Connections			
<ul> <li>Supply input</li> </ul>	L1/+, L2/N/-; PE PushIn for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	L1/+, L2/N/-; PE PushIn for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	L1/+, L2/N/-; PE PushIn for 0.5 4 mm <sup>2</sup> single-core/finely stranded
• Output	+1, -1, -2: PushIn for 0.5 2.5 mm <sup>2</sup>	+1, -1, -2: PushIn for 0.5 2.5 mm <sup>2</sup>	+1, +2, -1, -2, -3: PushIn for 0.5 2.5 mm <sup>2</sup>
Auxiliary	-	-	13, 14 (alarm signal): 1 push-in terminal each for 0.2 1.5 mm <sup>2</sup>
Width of the enclosure	25 mm	40 mm	35 mm
Height of the enclosure	100 mm	100 mm	135 mm
Depth of the enclosure	88 mm	88 mm	125 mm
Required spacing			
• top	50 mm	50 mm	45 mm
• bottom	50 mm	50 mm	45 mm
• left	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm
Product feature of the enclosure nousing for side-by-side mounting	Yes	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
Electrical accessories	Redundancy module	Redundancy module	Redundancy module
Mechanical accessories	SIMATIC ET 200SP equipment labels: 6ES7193-6LF30-0AW0	SIMATIC ET 200SP equipment labels: 6ES7193-6LF30-0AW0	SIMATIC ET 200SP equipment lat 6ES7193-6LF30-0AW0
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input volta and ambient temperature +25 °C (unless otherwise specified)

1) Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Article number	6EP3333-7SB00-0AX0 <sup>1)</sup>	6EP3334-7SB00-3AX0 <sup>1)</sup>	6EP3336-7SB00-3AX0 <sup>1)</sup>
Product	SITOP PSU6200	SITOP PSU6200	SITOP PSU6200
Power supply, type	24 V/5 A	24 V/10 A	24 V/20 A
Input			
Input	1-phase AC or DC	1-phase AC or DC	1-phase AC or DC
Rated voltage value Vin rated	120 230 V	120 230 V	120 230 V
Voltage range AC	85 264 V	85 264 V	85 264 V
Supply voltage			
• at DC	120 240 V	110 240 V	110 240 V
Input voltage			
• at DC	99 275 V	85 275 V	85 275 V
Wide-range input	Yes	Yes	Yes
Overvoltage resistance	300 V AC for 30 s	300 V AC for 30 s	300 V AC for 30 s
Mains buffering at I <sub>out rated</sub> , min.	80 ms; at V <sub>in</sub> = 230 V	45 ms; at V <sub>in</sub> = 230 V	25 ms; at V <sub>in</sub> = 230 V
Rated line frequency 1	50 Hz	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz	47 63 Hz
Input current			
<ul> <li>at rated input voltage 120 V</li> </ul>	1.9 A	2.2 A	4.3 A
<ul> <li>at rated input voltage 230 V</li> </ul>	1.1 A	1.2 A	2.3 A
Switch-on current limiting (+25 °C), max.	29 A	6 A	12 A
Built-in incoming fuse	3.15 A	5 A	10 A

3

# Standard power supplies SITOP PSU6200

# 1-phase, 24 V DC

## Technical specifications (continued)

Article number	6EP3333-7SB00-0AX0 <sup>1)</sup>	6EP3334-7SB00-3AX0 <sup>1)</sup>	6EP3336-7SB00-3AX0 <sup>1)</sup>
Product	SITOP PSU6200	SITOP PSU6200	SITOP PSU6200
Power supply, type	24 V/5 A	24 V/10 A	24 V/20 A
Output			
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Number of outputs	1	1	1
Rated voltage Vout rated DC	24 V	24 V	24 V
Total tolerance, static $\pm$	3 %	3 %	3 %
Static mains compensation, approx.	0.1 %	0.1 %	0.2 %
Static load balancing, approx.	0.2 %	0.1 %	0.2 %
Residual ripple peak-peak, max.	30 mV	30 mV	80 mV
Residual ripple peak-peak, typ.	20 mV	20 mV	50 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	100 mV	30 mV	100 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	60 mV	20 mV	60 mV
Adjustment range	24 28 V	24 28 V	24 28 V
Product function Output voltage adjustable	Yes	Yes	Yes
Output voltage setting	via potentiometer; max. 120 W (144 W up to 45°C)	via potentiometer; max. 240 W (288 W up to 45°C)	via potentiometer; max. 480 W (576 W up to 45°C)
Status display	Green LED for 24 V OK	Green LED for 24 V OK	Green LED for 24 V OK
Signaling	Electronic contact (NO contact, contact rating 60 V DC/0.1 A) for 24 V O.K. or diagnostic interface	Electronic contact (NO contact, contact rating 60 V DC/0.1 A) for 24 V O.K. or diagnostic interface	Electronic contact (NO contact, contact rating 60 V DC/0.1 A) for 24 V O.K. or diagnostic interface
On/off behavior	Overshoot of $V_{out} < 2 \%$	Overshoot of $V_{out} < 2 \%$	Overshoot of Vout approx. 3 %
Startup delay, max.	0.5 s	0.5 s	0.5 s
Voltage rise, typ.	100 ms	200 ms	100 ms
Rated current value Iout rated	5 A	10 A	20 A
Current range	0 5 A	0 10 A	0 20 A
Note	6 A up to +45°C; +60 +70 °C: Derating 2%/K	12 A up to +45°C; +60 +70 °C: Derating 2%/K	24 A up to +45°C; +60 +70 °C: Derating 1%/K
Supplied active power typical	120 W	240 W	480 W
Short-term overload current			
<ul> <li>on short-circuiting during the start- up typical</li> </ul>	6 A	12 A	30 A
<ul> <li>at short-circuit during operation typical</li> </ul>	6 A	12 A	30 A
Product feature parallel switching of outputs	-	can be set with DIP switch	can be set with DIP switch
Parallel switching for enhanced performance	-	switchable characteristic	Yes; switchable characteristic
Numbers of parallel switchable units for enhanced performance	-	2	2
Efficiency			
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	90.2 %	92.8 %	95.1 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	13 W	18 W	25 W
Power loss [W] during no-load operation maximum	2 W	2.2 W	2.6 W
Closed-loop control Dynamic load smoothing	2 %	2 %	3 %
(I <sub>out</sub> : 10/90/10 %), U <sub>out</sub> ± typ.			
Load step setting time 10 to 90%, typ.		2 ms	0.5 ms
Load step setting time 90 to 10%, typ.		2 ms	0.5 ms
Setting time maximum	2 ms	3 ms	1 ms
Protection and monitoring	< 22.)/	< 20 M	< 22 \/
Output overvoltage protection	< 32 V	< 32 V	< 32 V
Current limitation, typ.	6 A	12 A	30 A
Property of the output Short-circuit proof	Yes	Yes	Yes
Short-circuit protection	Shutdown and periodic restart attempts	Shutdown and periodic restart attempts	Shutdown and periodic restart attempts
Overcurrent overload capability in normal operation	overload capability 150 % <i>I</i> <sub>out rated</sub> up to 5 s/min	overload capability 150 % <i>l</i> <sub>out rated</sub> up to 5 s/min	overload capability 150 % <i>I</i> <sub>out rated</sub> up to 5 s/min

Article number	6EP3333-7SB00-0AX0 <sup>1)</sup>	6EP3334-7SB00-3AX0 <sup>1)</sup>	6EP3336-7SB00-3AX0 <sup>1)</sup>
Product	SITOP PSU6200	SITOP PSU6200	SITOP PSU6200
Power supply, type	24 V/5 A	24 V/10 A	24 V/20 A
Safety			
Primary/secondary isolation	Yes	Yes	Yes
Galvanic isolation	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Safety extra low output voltage $V_{\rm OL}$ according to EN 60950-1
Protection class	Class I	Class I	Class I
Leakage current			
• maximum	3.5 mA	3.5 mA	3.5 mA
CE mark	Yes	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	CULus-Listed (UL 508, CSA C22.2 107.1), File E197259; cCSAus (CS C22.2 No. 60950-1, UL 60950-1)
Explosion protection	-	-	-
FM approval	-	-	-
CB approval	Yes	Yes	Yes
Regulatory Compliance Mark (RCM)	No	No	No
Marine approval	in process: DNV GL, ABS	in process: DNV GL, ABS	in process: DNV GL, ABS
Degree of protection (EN 60529)	IP20	IP20	IP20
EMC			
Emitted interference	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2	EN 61000-3-2	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data			
Ambient temperature			
<ul> <li>during operation</li> </ul>	-25 +70 °C	-25 +70 °C	-25 +70 °C
- Note	with natural convection	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics			
Connection technology	Push-in terminals	Push-in terminals	Push-in terminals
Connections			
<ul> <li>Supply input</li> </ul>	L1/+, L2/N/-; PE PushIn for 0.5 4 mm <sup>2</sup> single-core/ finely stranded	L1/+, L2/N/-; PE PushIn for 0.5 4 mm <sup>2</sup> single-core/ finely stranded	L1/+, L2/N/-; PE PushIn for 0.5 4 mm <sup>2</sup> single- finely stranded
• Output	+1, +2, -1, -2, -3: PushIn for 0.5 2.5 mm <sup>2</sup>	+1, +2, -1, -2, -3: PushIn for 0.5 2.5 mm <sup>2</sup>	+1, +2, -1, -2, -3: PushIn for 0.5 6 mm <sup>2</sup>
Auxiliary	13, 14 (alarm signal): 1 push-in terminal each for 0.2 1.5 mm <sup>2</sup>	13, 14 (alarm signal): 1 push-in terminal each for 0.2 1.5 mm <sup>2</sup>	13, 14 (alarm signal): 1 push-in terminal each for 0.2 1.5 mm <sup>2</sup>
Width of the enclosure	35 mm	45 mm	70 mm
Height of the enclosure	135 mm	135 mm	135 mm
Depth of the enclosure	125 mm	125 mm	155 mm
Required spacing			
• top	45 mm	45 mm	45 mm
• bottom	45 mm	45 mm	45 mm
• left	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
Electrical accessories	SEL module, redundancy module	SEL module, redundancy module	SEL module, redundancy module
Mechanical accessories	SIMATIC ET 200SP equipment labels: 6ES7193-6LF30-0AW0	SIMATIC ET 200SP equipment labels: 6ES7193-6LF30-0AW0	SIMATIC ET 200SP equipment lab 6ES7193-6LF30-0AW0

1) Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

# Standard power supplies

SITOP PSU6200

## 1-phase, 24 V DC

B

Ordering data	Article No.	Accessories	Article No.
SITOP PSU6200 1-phase, 24 V DC/1.3 A	6EP3331-7SB00-0AX0	SITOP RED1200 redundancy module	6EP4346-7RB00-0AX0
Stabilized power supply Input: 120–230 V AC/120–240 V DC Output: 24 V DC/1.3 A		Input/output: 12 V DC, 24 V, 48 V/20 A (maximum total current) Suitable for decoupling two SITOP	
SITOP PSU6200 1-phase, 24 V DC/2.5 A	6EP3332-7SB00-0AX0	power supplies with a maximum of 10 A output current each	
Stabilized power supply Input: 120–230 V AC/120–240 V DC		SITOP RED1200 redundancy module	6EP4347-7RB00-0AX0
Output: 24 V DC/2.5 A		Input/output: 12 V DC, 24 V,	
SITOP PSU6200 1-phase, 24 V DC/3.7 A	6EP3333-7LB00-0AX0	48 V/40 A (maximum total current) Suitable for decoupling two SITOP power supplies with a maximum of	
Stabilized power supply		20 A output current each	
Input: 120–230 V AC/120–240 V DC Output: 24 V DC/3.7 A		SITOP SEL1200	6EP4438-7FB00-3DX0
SITOP PSU6200 1-phase, 24 V DC/5 A	6EP3333-7SB00-0AX0	Selectivity module, 8-channel, switching Input: 24 V DC	
Stabilized power supply Input: 120–230 V AC/120–240 V DC Output: 24 V DC/5 A		Output: 24 V DC/10 A per output Adjustable response threshold 2 10 A	
SITOP PSU6200, 1-phase	6EP3334-7SB00-3AX0	SITOP SEL1400	6EP4438-7EB00-3DX0
24 V DC/10 A		Selectivity module, 8-channel,	
Stabilized power supply Input: 120–230 V AC/110–240 V DC Output: 24 V DC/10 A		limiting Input: 24 V DC Output: 24 V DC/10 A per output Adjustable response threshold	
SITOP PSU6200, 1-phase, 24 V DC/20 A	6EP3336-7SB00-3AX0	2 10 A	
Stabilized power supply nput: 120–230 V AC/110–240 V DC		SIMATIC ET 200SP equipment labels	6ES7193-6LF30-0AW0
Output: 24 V DC/20 A		160 equipment labeling plates, 10 sheets (160 labels)	

### More information

Select the appropriate power supply quickly and easily with the TIA Selection Tool: http://www.siemens.com/tst

Standard power supplies SITOP smart

#### Introduction

#### Overview



#### The powerful standard power supply

The single-phase and three-phase SITOP smart are the universal and powerful standard power supplies for machinery and plant engineering. Despite their compact design, they offer an excellent overload response: Thanks to a power boost of 150%, loads with high power consumption can be connected without any problems and the permanent overload capability of 120% offers power reserves in case of expansions. The high degree of efficiency results in low energy consumption and minimal heat generation inside the control cabinet.

To further increase the 24 V availability, the SITOP smart power supplies can be combined with buffer, DC UPS, redundancy and selectivity modules.

#### Main product highlights

- 1-phase, 24 V DC/2.5 A, 5 A, 10 A and 20 A as well as 12 V/7 A and 14 A
- 3-phase, 24 V DC/5 A, 10 A, 20 A and 40 A
- Compact design no lateral clearances required
- Extra power with 1.5 times the rated current (5 s/min) for brief functional overload
- Permanent overload capability with 1.2 times the rated current up to 45 °C ambient temperature (24 V versions)
- High degree of efficiency up to 91.5%
- Adjustable output voltage for compensating voltage drops
- Signaling contact for easy integration in the plant monitoring system
- Wide temperature range from -25 or −10 to +70 °C
- Comprehensive certifications, such as cULus, cCSAus, ATEX, IECEx and DNV GL

## More information

Select the appropriate power supply guickly and easily with the TIA Selection Tool:

http://www.siemens.com/tst

#### Standard power supplies

SITOP smart

### Overview



The single-phase SITOP smart are the universal and powerful standard power supplies for machinery and plant engineering. Despite their compact design, they offer an excellent overload response: Thanks to a power boost of 150%, loads with high power consumption can be connected without any problems. The high degree of efficiency results in low energy consumption and minimal heat generation inside the control cabinet.

#### Main product highlights

- 1-phase, 12 V DC/7 A and 14 A
- Input voltage 120 V and 230 V AC with automatic range switching
- Compact design no lateral clearances required
- Extra power with 1.5 times the rated current (5 s/min) for brief functional overload
- Adjustable output voltage for compensating voltage drops
- Signaling contact for easy integration in the plant monitoring system
- Wide temperature range from -25 to +70 °C
- Comprehensive certifications, such as cULus, cCSAus, ATEX, IECEx and DNV GL

#### Technical specifications

Article number	6EP1322-2BA00 <sup>1)</sup>	6EP1323-2BA00 <sup>1)</sup> SITOP PSU100S	
Product	SITOP PSU100S		
Power supply, type	12 V/7 A	12 V/14 A	
Input			
Input	1-phase AC	1-phase AC	
Note	Automatic range selection	Automatic range selection	
Supply voltage			
<ul> <li>1 at AC Rated value</li> </ul>	120 V	120 V	
<ul> <li>2 at AC Rated value</li> </ul>	230 V	230 V	
Input voltage			
• 1 at AC	85 132 V	85 132 V	
• 2 at AC	170 264 V	170 264 V	
Wide-range input	No	No	
Overvoltage resistance	$2.3 \times V_{\text{in rated}}$ , 1.3 ms	$2.3 \times V_{\text{in rated}}$ , 1.3 ms	
Mains buffering at I <sub>out rated</sub> , min.	20 ms; at V <sub>in</sub> = 93/187 V	20 ms; at V <sub>in</sub> = 93/187 V	
Rated line frequency 1	50 Hz	50 Hz	
Rated line frequency 2	60 Hz	60 Hz	
Rated line range	47 63 Hz	47 63 Hz	
Input current			
<ul> <li>at rated input voltage 120 V</li> </ul>	1.73 A	3.24 A	
<ul> <li>at rated input voltage 230 V</li> </ul>	0.99 A	1.41 A	
Switch-on current limiting (+25 °C), max.	45 A	60 A	
Built-in incoming fuse	T 3,15 A/250 V (not accessible)	T 6.3 A/250 V (not accessible)	
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 6 A characteristic C	Recommended miniature circuit breaker: from 10 A characteristic C	
Dutput			
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage	
Rated voltage Vout rated DC	12 V	12 V	
Total tolerance, static $\pm$	3 %	3 %	
Static mains compensation, approx.	0.1 %	0.1 %	
Static load balancing, approx.	1 %	1 %	
Residual ripple peak-peak, max.	150 mV	150 mV	

Standard power supplies SITOP smart

1-phase, 12 V DC

Article number	6EP1322-2BA00 <sup>1)</sup>	6EP1323-2BA00 <sup>1)</sup>
Product	SITOP PSU100S	SITOP PSU100S
Power supply, type	12 V/7 A	12 V/14 A
Dutput (continued)		
Residual ripple peak-peak, typ.	20 mV	20 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	240 mV	240 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	100 mV	100 mV
Adjustment range	11.5 15.5 V	11.5 15.5 V
Product function Output voltage adjustable	Yes	Yes
Output voltage setting	via potentiometer	via potentiometer
Status display	Green LED for 12 V OK	Green LED for 12 V OK
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for 12 V OK	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for 12 V OK
On/off behavior	Overshoot of $V_{out} < 3 \%$	Overshoot of $V_{out} < 3 \%$
Startup delay, max.	0.3 s	0.3 s
Voltage rise, typ.	10 ms	10 ms
Rated current value <i>l</i> out rated	7 A	14 A
Current range	0 7 A	0 14 A
Note	+50 +70 °C: Derating 0.75%/K	+50 +70 °C: Derating 3.5%/K
Supplied active power typical	84 W	168 W
Short-term overload current <ul> <li>on short-circuiting during the start-</li> </ul>	25 A	40 A
up typical • at short-circuit during operation	25 A	40 A
typical Duration of overloading capability for		
<ul><li>excess current</li><li>on short-circuiting during the start-</li></ul>	800 ms	800 ms
up <ul> <li>at short-circuit during operation</li> </ul>	800 ms	800 ms
Parallel switching for enhanced performance	Yes	Yes
Numbers of parallel switchable units for enhanced performance	2	2
Efficiency		
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	84 %	87 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	15 W	24 W
Closed-loop control		
Dynamic load smoothing ( <i>l<sub>out</sub></i> : 10/90/10 %), <i>U<sub>out</sub> ±</i> typ.	5 %	5 %
Load step setting time 10 to 90%, typ	. 1 ms	1 ms
Load step setting time 90 to 10%, typ	. 1 ms	1 ms
Protection and monitoring		
Output overvoltage protection	< 20 V	< 20 V
Current limitation	7 8.8 A	14 16.4 A
Property of the output Short-circuit proof	Yes	Yes
Short-circuit protection Enduring short circuit current RMS value	Constant current characteristic	Constant current characteristic
typical	8.8 A	16.4 A
Overcurrent overload capability in normal operation	overload capability 150 % Iout rated up to 5 s/min	overload capability 150 % <i>I</i> <sub>out rated</sub> up to 5 s/min
Overload/short-circuit indicator	-	_
Safety		
Primary/secondary isolation	Yes	Yes
Galvanic isolation	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950- and EN 50178
Protection class	Class I	Class I
Leakage current		
• maximum	3.5 mA	3.5 mA
	0.4 mA	0.8 mA

# Standard power supplies

SITOP smart

# 1-phase, 12 V DC

## Technical specifications (continued)

Article number	6EP1322-2BA00 <sup>1)</sup>	6EP1323-2BA00 <sup>1)</sup>
Product	SITOP PSU100S	SITOP PSU100S
Power supply, type	12 V/7 A	12 V/14 A
Safety (continued)		
CE mark	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259, cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	CULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259, cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
Explosion protection	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cULus Class I Div. 2 (ANSI/ISA-12.12.01-2007, CSA C22.2 No. 213) Group ABCD, T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cULus Class I Div. 2 (ANSI/ISA-12.12.01-2007, CSA C22.2 No. 213) Group ABCD, T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4
FM approval	-	-
CB approval	Yes	Yes
Marine approval	DNV GL	DNV GL
Degree of protection (EN 60529)	IP20	IP20
EMC		
Emitted interference	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2
Operating data		
Ambient temperature		
during operation	-25 +70 °C	-25 +70 °C
- Note	with natural convection	with natural convection
during transport	-40 +85 °C	-40 +85 °C
during storage	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics		
Connection technology	screw-type terminals	screw-type terminals
Connections		
Supply input	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded
Output	+, -: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup>	+, -: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup>
Auxiliary	Alarm signals: 2 screw terminals for 0.5 2.5 mm <sup>2</sup>	Alarm signals: 2 screw terminals for 0.5 2.5 mm <sup>2</sup>
Connections signaling contact	2 screw terminals for 0.5 2.5 mm <sup>2</sup>	2 screw terminals for 0.5 2.5 mm <sup>2</sup>
Width of the enclosure	50 mm	70 mm
Height of the enclosure	125 mm	125 mm
Depth of the enclosure	120 mm	120 mm
Required spacing		
• top	50 mm	50 mm
bottom	50 mm	50 mm
• left	0 mm	0 mm
• right	0 mm	0 mm
Weight, approx.	0.5 kg	0.7 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
MTBF at 40 °C	1 998 441 h	1 614 510 h
	$\sim$ 25 °C (uplace otherwise specific	

1) Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Ordering data	Article No.	More information
SITOP PSU100S 1-phase, 12 V DC/7 A	6EP1322-2BA00	Select the appropriate power supply quickly and easily with the TIA Selection Tool:
Stabilized power supply Input: 120/230 V AC Output: 12 V DC/7 A		http://www.siemens.com/tst
SITOP PSU100S 1-phase, 12 V DC/14 A	6EP1323-2BA00	
Stabilized power supply Input: 120/230 V AC Output: 12 V DC/14 A		
Accessories:		
SITOP redundancy RED1200 modules	see page 9/6	

3/18 Siemens KT 10.1 · 2019/2020

### Overview



The single-phase SITOP smart are the universal and powerful standard power supplies for machinery and plant engineering. Despite their compact design, they offer an excellent overload response: Thanks to a power boost of 150%, loads with high power consumption can be connected without any problems and the permanent overload capability of 120% offers power reserves in case of expansions. The high degree of efficiency results in low energy consumption and minimal heat generation in side the control cabinet.

To further increase 24 V availability, the SITOP smart power supplies can be combined with **buffer**, **DC UPS**, **redundancy** and **selectivity modules**.

### Main product highlights

- 1-phase, 24 V DC/2.5 A, 5 A, 10 A and 20 A
- Input voltage 120 V and 230 V AC with automatic range switching
- Compact design-no lateral clearances required
- Extra power with 1.5 times the rated current (5 s/min) for brief functional overload
- Permanent overload capability with 1.2 times the rated current up to 45 °C ambient temperature
- Adjustable output voltage for compensating voltage drops
- Signaling contact for easy integration in the plant monitoring system
- Wide temperature range from -25 or 0 to +70 °C
- Comprehensive certifications, such as cULus, cCSAus, ATEX, IECEx and DNV GL

### Technical specifications

Article number	6EP1332-2BA20 <sup>1)</sup>	6EP1333-2BA20 <sup>1)</sup>	6EP1334-2BA20 <sup>1)</sup>	6EP1336-2BA10 <sup>1)</sup>
Product	SITOP PSU100S	SITOP PSU100S	SITOP PSU100S	SITOP PSU100S
Power supply, type	24 V/2.5 A	24 V/5 A	24 V/10 A	24 V/20 A
Input				
Input	1-phase AC	1-phase AC	1-phase AC	1-phase AC
Note	Automatic range selection	Automatic range selection	Automatic range selection	Automatic range selection
Supply voltage				
<ul> <li>1 at AC Rated value</li> </ul>	120 V	120 V	120 V	120 V
<ul> <li>2 at AC Rated value</li> </ul>	230 V	230 V	230 V	230 V
Input voltage				
• 1 at AC	85 132 V	85 132 V	85 132 V	85 132 V
• 2 at AC	170 264 V	170 264 V	170 264 V	176 264 V
Wide-range input	No	No	No	No
Overvoltage resistance	$2.3 \times V_{\rm in \ rated}$ , 1.3 ms	$2.3 \times V_{\rm in \ rated}$ , 1.3 ms	$2.3 \times V_{\text{in rated}}$ , 1.3 ms	$2.3 \times V_{\rm in \ rated}$ , 1.3 ms
Mains buffering at Iout rated, min.	20 ms; at V <sub>in</sub> = 93/187 V	20 ms; at V <sub>in</sub> = 93/187 V	20 ms; at V <sub>in</sub> = 93/187 V	20 ms; at V <sub>in</sub> = 120/230 V
Rated line frequency 1	50 Hz	50 Hz	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz	47 63 Hz	47 63 Hz
Input current				
<ul> <li>at rated input voltage 120 V</li> </ul>	1.25 A	2.34 A	4.49 A	7.5 A
<ul> <li>at rated input voltage 230 V</li> </ul>	0.74 A	1.36 A	1.91 A	3.5 A
Switch-on current limiting (+25 °C), max.	33 A	40 A	60 A	11 A
l²t, max.	0.4 A <sup>2</sup> ·s	1 A <sup>2</sup> ·s	5.6 A <sup>2.</sup> s	10 A <sup>2</sup> ·s
Built-in incoming fuse	T 3,15 A/250 V (not accessible)	T 3,15 A/250 V (not accessible)	T 6.3 A/250 V (not accessible)	T 10 A (not accessible)
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 3 A characteristic C	Recommended miniature circuit breaker: from 6 A characteristic C	Recommended miniature circuit breaker: from 10 A characteristic C	Recommended miniature circuit breaker: from 10 A characteristic C or circuit- breaker 3RV2411-1JA10 (120 V) or 3RV2411-1FA10 (230 V)

# Standard power supplies SITOP smart

# 1-phase, 24 V DC

Article number	6EP1332-2BA20 <sup>1)</sup>	6EP1333-2BA20 <sup>1)</sup>	6EP1334-2BA20 <sup>1)</sup>	6EP1336-2BA10 <sup>1)</sup>
Product	SITOP PSU100S	SITOP PSU100S	SITOP PSU100S	SITOP PSU100S
Power supply, type	24 V/2.5 A	24 V/5 A	24 V/10 A	24 V/20 A
Output				
Output	Controlled, isolated DC voltage			
Rated voltage Vout rated DC	24 V	24 V	24 V	24 V
Total tolerance, static ±	3 %	3 %	3 %	3 %
Static mains compensation, approx.	0.1 %	0.1 %	0.1 %	0.5 %
Static load balancing, approx.	1 %	1 %	1 %	1 %
Residual ripple peak-peak, max.	150 mV	150 mV	150 mV	150 mV
Residual ripple peak-peak, typ.	30 mV	30 mV	20 mV	
Spikes peak-peak, max. (bandwidth: 20 MHz)	240 mV	240 mV	240 mV	240 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	70 mV	140 mV	160 mV	
Adjustment range	22.8 28 V	22.8 28 V	22.8 28 V	24 28 V
Product function Output voltage adjustable	Yes	Yes	Yes	Yes
Output voltage setting	via potentiometer	via potentiometer	via potentiometer	via potentiometer; max. 480 W
Status display	Green LED for 24 V OK			
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"
On/off behavior	Overshoot of $V_{\rm out}$ < 3 %	Overshoot of $V_{\rm out}$ < 3 %	Overshoot of $V_{\rm out}$ < 3 %	No overshoot of V <sub>out</sub> (soft start)
Startup delay, max.	0.3 s	0.3 s	0.3 s	1.5 s
Voltage rise, typ.	15 ms	15 ms	20 ms	50 ms
Voltage increase time of the output voltage maximum				500 ms
Rated current value Iout rated	2.5 A	5 A	10 A	20 A
Current range	0 3 A	0 6 A	0 12 A	0 20 A
Note	3 A up to +45°C; +60 +70 °C: Derating 3%/K	6 A up to +45°C; +60 +70 °C: Derating 1.6%/K	12 A up to +45°C; +60 +70 °C: Derating 3%/K	24 A up to +45°C; +60 +70 °C: Derating 5%/K
Supplied active power typical	60 W	144 W	288 W	480 W
Short-term overload current				
<ul> <li>on short-circuiting during the start- up typical</li> </ul>	9 A	18 A	32 A	35 A
<ul> <li>at short-circuit during operation typical</li> </ul>	9 A	18 A	32 A	35 A
Duration of overloading capability for excess current				
<ul> <li>on short-circuiting during the start- up</li> </ul>	100 ms	800 ms	1 000 ms	100 ms
<ul> <li>at short-circuit during operation</li> </ul>	800 ms	800 ms	1 000 ms	100 ms
Parallel switching for enhanced performance	Yes	Yes	Yes	Yes
Numbers of parallel switchable units for enhanced performance	2	2	2	2
Efficiency				
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	85 %	88 %	90 %	90 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	10 W	16 W	25 W	53 W

# Standard power supplies SITOP smart

1-phase, 24 V DC

Article number	6EP1332-2BA20 <sup>1)</sup>	6EP1333-2BA20 <sup>1)</sup>	6EP1334-2BA20 <sup>1)</sup>	6EP1336-2BA10 <sup>1)</sup>
Product	SITOP PSU100S	SITOP PSU100S	SITOP PSU100S	SITOP PSU100S
Power supply, type	24 V/2.5 A	24 V/5 A	24 V/10 A	24 V/20 A
Closed-loop control				
Dynamic mains compensation ( <i>V<sub>in rated</sub></i> ±15 %), max.	0.3 %	0.3 %	0.3 %	1 %
Dynamic load smoothing ( <i>I</i> <sub>out</sub> : 50/100/50 %), <i>U</i> <sub>out</sub> ± typ.	-	-	-	3 %
Dynamic load smoothing (/ <sub>out</sub> : 10/90/10 %), <i>U</i> <sub>out</sub> ± typ.	5 %	3 %	3 %	-
Load step setting time 10 to 90%, typ.	1 ms	1 ms	1 ms	-
Load step setting time 90 to 10%, typ.	1 ms	1 ms	1 ms	-
Setting time maximum	-	-	-	10 ms
Protection and monitoring				
Output overvoltage protection	protection against overvoltage in case of internal fault $V_{out} < 33$ V	protection against overvoltage in case of internal fault $V_{out}$ < 33 V	protection against overvoltage in case of internal fault $V_{out} < 33$ V	Yes, according to EN 60950-1
Current limitation	3 3.4 A	6 7.1 A	12 14.6 A	-
Current limitation, typ.	-	-	-	21 A
Property of the output Short-circuit proof	Yes	Yes	Yes	Yes
Short-circuit protection	Constant current character- istic	Constant current character- istic	Constant current character- istic	Electronic shutdown, automatic restart
Enduring short circuit current RMS value				
• maximum	-	-	-	7 A
• typical	3.4 A	7.1 A	14.6 A	-
Overcurrent overload capability in normal operation	overload capability 150 % I <sub>out rated</sub> up to 5 s/min	overload capability 150 % I <sub>out rated</sub> up to 5 s/min	overload capability 150 % I <sub>out rated</sub> up to 5 s/min	overload capability 150 I <sub>out rated</sub> up to 5 s/min
Overload/short-circuit indicator	-	-	-	-
Safety				
Primary/secondary isolation	Yes	Yes	Yes	Yes
Galvanic isolation	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage $U_{out}$ acc. to EN 60950-1 and EN 501
Protection class	Class I	Class I	Class I	Class I
Leakage current				
• maximum	3.5 mA	3.5 mA	3.5 mA	3.5 mA
• typical	0.4 mA	0.4 mA	0.8 mA	1 mA
CE mark	Yes	Yes	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259, cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	CULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259, cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259, cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259, cCSAus (CSA C22.2 No. 60950-1 UL 60950-1)
Explosion protection	T4 Gc; cÚLus Class I Div. 2 (ANSI/ISA-12.12.01-2007, CSA C22.2 No. 213-M1987) Group ABCD, T4; cCSAus (CSA C22.2 No. 213, ANSI/	IECEX EX NA NC IIC T4 GC; ATEX (EX) II 3G EX NA NC IIC T4 Gc; CULus Class I Div. 2 (ANSI/ISA-12.12.01-2007, CSA C22.2 No. 213-M1987) Group ABCD, T4; cCSAus (CSA C22.2 No. 213, ANSI/ ISA-12. 12.01) Class I, Div. 2, Group ABCD, T4	IECEX EX NA NC IIC T4 GC; ATEX (EX) II 3G EX NA NC IIC T4 GC; CULus Class I Div. 2 (ANSI/ISA-12.12.01-2007, CSA C22.2 No. 213-M1987) Group ABCD, T4; CCSAus (CSA C22.2 No. 213, ANSI/ ISA-12. 12.01) Class I, Div. 2, Group ABCD, T4	IECEX EX NA NC IIC T4 G ATEX (EX) II 3G EX NA NC T4 GC; CCSAUS (CSA C2 No. 213, ANSI/ISA-12.12 Class I, Div. 2, Group AB T4
FM approval	-	-	-	-
CB approval	Yes	Yes	Yes	Yes
Marine approval	BV, DNV GL	BV, DNV GL	BV, DNV GL	DNV GL
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20

# Standard power supplies

SITOP smart

## 1-phase, 24 V DC

## Technical specifications (continued)

ProductSTOP PSU100SSTOP PSU100SSTOP PSU100SSTOP PSU100SSTOP PSU100SPower supply, type24 V/2.5 A24 V/10 A24 V/20 AEMC </th <th>Article number</th> <th>6EP1332-2BA20<sup>1)</sup></th> <th>6EP1333-2BA20<sup>1)</sup></th> <th>6EP1334-2BA20<sup>1)</sup></th> <th>6EP1336-2BA10<sup>1)</sup></th>	Article number	6EP1332-2BA20 <sup>1)</sup>	6EP1333-2BA20 <sup>1)</sup>	6EP1334-2BA20 <sup>1)</sup>	6EP1336-2BA10 <sup>1)</sup>	
EMC         Entred         Entred interference         EN 55022 Class B         EN 5502 Class B         EN 5502           40	Product	SITOP PSU100S	SITOP PSU100S	SITOP PSU100S	SITOP PSU100S	
Emitted interference         EN 55022 Class B         EN 5502 Class B <th>Power supply, type</th> <th>24 V/2.5 A</th> <th>24 V/5 A</th> <th>24 V/10 A</th> <th>24 V/20 A</th>	Power supply, type	24 V/2.5 A	24 V/5 A	24 V/10 A	24 V/20 A	
Supply harmonics limitation Noise immunitynot applicable EN 81000-6-2EN 81000-6-2EN 81000-6-2EN 81000-6-2EN 81000-6-2Operating dat - during operation	EMC					
Noise immunityEN 61000-6-2EN 61000-6-2EN 61000-6-2EN 61000-6-2Operating dat Ambient temperature duing operation070 °C- Notewith natural convectionwith natural convection070 °C-070 °C-070 °C070 °C070 °C070 °C070 °C-070 °C-070 °C070 °C-070 °C070 °C	Emitted interference	EN 55022 Class B				
Operating data         Ambient temperature	Supply harmonics limitation	not applicable	EN 61000-3-2	EN 61000-3-2	EN 61000-3-2	
Ambient imperature • during operation-25+70 °C-25+70 °C-40+85 °C-40	Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	
• during operation $-25 \dots + 70  ^{\circ} C$ $-25 \dots + 70  ^{\circ} C$ $-25 \dots + 70  ^{\circ} C$ $0 \dots , 70  ^{\circ} C$ · Notewith natural convectionwith natural convectionwith natural convectionwith natural convection· during storage $-40 \dots + 85  ^{\circ} C$ · during storage· $-40 \dots + 85  ^{\circ} C$ · BorzelClimate class 3K3, no condensationconcondensationno condensationno condensation· Roberscrew-type terminalsscrew-type terminalsscrew-type terminalsscrew-type terminals· Connection s	Operating data					
- Notewith natural convectionwith natural convectionwith natural convectionwith natural convection4 during transport-40+85 °C-40+85 °C-40+85 °C-40+85 °C4 during transport	Ambient temperature					
• during transport $40 \dots +85  {}^{\circ}{\rm C}$ $40 \dots +85  {}^{\circ}{\rm C$	<ul> <li>during operation</li> </ul>	-25 +70 °C	-25 +70 °C	-25 +70 °C	0 70 °C	
• during storage+40 +85 °C-40 +85 °C-40 +85 °C-40 +85 °C-40 +85 °C-40 +85 °C-40 +85 °CClimate class 3K3, no condensationClimate class 3K3, no condensation• Output• Output <td>- Note</td> <td>with natural convection</td> <td>with natural convection</td> <td>with natural convection</td> <td>with natural convection</td>	- Note	with natural convection	with natural convection	with natural convection	with natural convection	
Humidity Lass according to EN 60721Climate class 3K3, no condensationClimate class 3K3, screw-terminalClimate class 3K3,	<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C	
EN 60721no condensationno condensationno condensationno condensationno condensationMechanics <td><ul> <li>during storage</li> </ul></td> <td>-40 +85 °C</td> <td>-40 +85 °C</td> <td>-40 +85 °C</td> <td>-40 +85 °C</td>	<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C	
Connection technology Connectionsscrew-type terminalsscrew-type terminalsscrew-type terminalsscrew-type terminalsSupply inputL, N, PE: 1 screw terminal each for 0.5 2.5 mm² single-core/linely strandedL, N, PE: 1 screw terminal each for 0.5 2.5 mm² single-core/linely strandedL, N, PE: 1 screw terminal each for 0.5 2.5 mm² single-core/linely strandedL, N, PE: 1 screw terminal each for 0.5 2.5 mm² single-core/linely strandedL, N, PE: 1 screw terminal each for 0.5 2.5 mm² single-core/linely strandedL, N, PE: 1 screw terminal each for 0.5 2.5 mm² single-core/linely strandedL, N, PE: 1 screw terminal each for 0.5 2.5 mm² single-core/linely strandedL, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²L, N, PE: 1 screw terminals each for 0.5 2.5 mm²						
ConnectionsAAASupply inputL, N, PE: 1 screw terminal each for 0.525 mm2L, N, PE: 1 screw terminals each for 0.525 mm2L, N, PE: 1 screw terminal each for 0.14L, N, PE: 1 screw terminal each for 0.14L, N, PE: 1 screw terminal screw terminal each for 0.14L, N, PE: 1 screw terminal each for 0.525 mm2L, N, PE:	Mechanics					
Supply inputL, N, PE: 1 screw terminal each for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminal each for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminal each for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminal each for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminal each for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminal each for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminal each for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminal each for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminal each for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminal seach for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminal seach for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminal seach for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminal seach for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminal seach for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminals each for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminals each for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminals each for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminals each for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminals each for 0.5 2.5 mm2 single-core/finely strandedL, N, PE: 1 screw terminals each for 0.5 2.5 mm2 single-core/finely strandedConnections signaling contact2 screw terminals for 0.5 2	Connection technology	screw-type terminals	screw-type terminals	screw-type terminals	screw-type terminals	
action of the serve for 0.5 2.5 mm² single-core/finely strandedeach for 0.5 2.5 mm² single-core/finely strandedeach for 0.5 2.5 mm² single-core/finely stranded• Output+, -: 2 sorew terminals each for 0.5 2.5 mm²+, -: 2 sorew terminals each for 0.2 4 mm²• AuxiliaryAlarr signals: 2 sorew terminals for 0.5 2.5 mm²Alarr signals: 2 sorew terminals for 0.5 2.5 mm²13, 14 (alarm signal): 1.5 sorew terminals each for 0.14 1.5 mm²Connections signaling contact2 sorew terminals for 0.5 2.5 mm²2 sorew terminals for 0.5 2.5 mm²13, 14 (alarm signal): 1.5 sorew terminals each for 0.14 1.5 mm²Width of the enclosure32.5 mm²2 sorew terminals for 0.5 2.5 mm²2 sorew terminals each for 0.14 1.5 mm²Height of the enclosure125 mm120 mm120 mm145 mmLequired spacing120 mm120 mm120 mm145 mm• top50 mm50 mm50 mm50 mm50 mm• top50 mm50 mm50 mm50 mm50 mm• top50 mm0 mm0 mm0 mm0 mm• top0.32 kg0.5 kg0.8 kg2.4 kg• top0.32 kg0.5 kgNeso top DIN	Connections					
for 0.5 2.5 mm²for 0.5 2.	Supply input	each for 0.5 2.5 mm <sup>2</sup>	each for 0.5 2.5 mm <sup>2</sup>	each for 0.5 2.5 mm <sup>2</sup>	each for 0.2 4 mm <sup>2</sup> single-	
terminals for 0.5 2.5 mm²terminals for 0.	Output					
Letter2.5 mm²2.5 mm²2.5 mm²2.5 mm²Width of the enclosure32.5 mm50 mm70 mm115 mmHeight of the enclosure125 mm125 mm125 mm145 mmDepth of the enclosure120 mm120 mm120 mm150 mmRequired spacing• top50 mm50 mm50 mm50 mm50 mm50 mm• bottom50 mm50 mm0 mm50 mm60 mm60 mm• left0 mm0 mm0 mm0 mm0 mm0 mm• right0 mm0.32 kg0.5 kg0.8 kg2.4 kgProduct feature of the enclosure ousing for side-by-side mountingSnaps onto DIN rail EN 60715 35x7.5/15Snaps onto DIN rail EN 60715 35x7.5/15<	Auxiliary				1 screw terminal each for	
Height of the enclosure125 mm125 mm125 mm145 mmDepth of the enclosure120 mm120 mm120 mm120 mm150 mmRequired spacing50 mm50 mm50 mm50 mm50 mm50 mm• top50 mm50 mm50 mm50 mm50 mm50 mm50 mm• bottom50 mm50 mm0 mm0 mm0 mm50 mm50 mm• left0 mm0 mm0 mm0 mm0 mm0 mm0 mm• right0 mm0.5 kg0.8 kg2.4 kg2.4 kgNedgt, approx.Ness onto DIN rail EN 60715 S5x7.5frSnaps onto DIN rail	Connections signaling contact					
o Required spacing120 mm120 mm120 mm150 mmi top50 mm50 mm50 mm50 mm50 mmi top50 mm50 mm50 mm50 mm50 mmi bottom50 mm0 mm0 mm50 mm50 mmi left0 mm0 mm0 mm0 mm0 mmi right0 mm0 mm0 mm0 mm0 mmWeight, approx.0.32 kg0.5 kg0.8 kg2.4 kgProduct feature of the enclosure housing for side-by-side mountingYesYesYesInstallationSnaps onto DIN rail EN 60715 35x7.5/15Snaps on	Width of the enclosure	32.5 mm	50 mm	70 mm	115 mm	
Acquired spacingInstantionInstantionInstantionInstantion• top50 mm50 mm50 mm50 mm50 mm• bottom50 mm50 mm50 mm50 mm50 mm• left0 mm0 mm0 mm0 mm0 mm• right0 mm0 mm0 mm0 mm0 mmWeight, approx.0.32 kg0.5 kg0.8 kg2.4 kg• roduct feature of the enclosure of the enclosure for Signer Sig	Height of the enclosure	125 mm	125 mm	125 mm	145 mm	
• top50 mm50 mm50 mm50 mm50 mm• bottom50 mm50 mm50 mm50 mm50 mm• left0 mm0 mm0 mm0 mm0 mm• right0 mm0 mm0 mm0 mm0 mmWeight, approx.0.32 kg0.5 kg0.8 kg2.4 kgProduct feature of the enclosure housing for side-by-side mouttingYesYesYesInstallationSnaps onto DIN rail EN 60715 35x7.5/15Snaps onto DIN rail EN 60715 35x7.5/15 <td>Depth of the enclosure</td> <td>120 mm</td> <td>120 mm</td> <td>120 mm</td> <td>150 mm</td>	Depth of the enclosure	120 mm	120 mm	120 mm	150 mm	
• bottom50 mm50 mm50 mm50 mm50 mm• left0 mm0 mm0 mm0 mm0 mm• right0 mm0 mm0 mm0 mm0 mmWeight, approx.0.32 kg0.5 kg0.8 kg2.4 kgProduct feature of the enclosure housing for side-by-side mountingYesYesYesInstallationSnaps onto DIN rail EN 60715 35x7.5/15Snaps onto DIN rail EN 60715 35x7	Required spacing					
• left0 mm0 mm0 mm0 mm• right0 mm0 mm0 mm0 mm0 mmWeight, approx.0.32 kg0.5 kg0.8 kg2.4 kgProduct feature of the enclosure housing for side-by-side mouttingYesYesYesInstallationSnaps onto DIN rail EN 60715 35x7.5/15Snaps onto DIN rail EN 60715 35x7.5/15Electrical accessoriesBuffer moduleBuffer moduleBuffer moduleBuffer moduleMechanical accessoriesDevice identification label 20 mm x 7 mm, TI-grey: 3RT2900-1SB20Device identification label 3RT2900-1SB20Device identification label 3RT2900-1SB20Snaps onto SB20	• top	50 mm	50 mm	50 mm	50 mm	
• right0 mm0 mm0 mm0 mmWeight, approx.0.32 kg0.5 kg0.8 kg2.4 kgProduct feature of the enclosure housing for side-by-side mountingYesYesYesInstallationSnaps onto DIN rail EN 60715 35x7.5/15Snaps onto DIN rail EN 60715 35x7.5/15Electrical accessoriesBuffer moduleBuffer moduleBuffer moduleBuffer moduleMechanical accessoriesDevice identification label 20 mm x 7 mm, TI-grey: 3RT2900-1SB20Device identification label 20 mm x 7 mm, TI-grey: 3RT2900-1SB20	bottom	50 mm	50 mm	50 mm	50 mm	
Weight, approx.0.32 kg0.5 kg0.8 kg2.4 kgProduct feature of the enclosure housing for side-by-side mountingYesYesYesYesInstallationSnaps onto DIN rail EN 60715 35x7.5/15Snaps onto DIN rail EN 60715 35x7.5/15Electrical accessoriesBuffer moduleBuffer moduleBuffer moduleBuffer moduleMechanical accessoriesDevice identification label 20 mm x 7 mm, TI-grey: 3RT2900-1SB20Device identification label 20 mm x 7 mm, TI-grey: 3RT2900-1SB20	• left	0 mm	0 mm	0 mm	0 mm	
Product feature of the enclosure housing for side-by-side mountingYesYesYesYesInstallationSnaps onto DIN rail EN 60715 35x7.5/15Snaps onto DIN rail EN 60715 35x7.5/15Electrical accessoriesBuffer moduleBuffer moduleBuffer moduleBuffer moduleMechanical accessoriesDevice identification label 20 mm x 7 mm, TI-grey: 3RT2900-1SB20Device identification label 20 mm x 7 mm, TI-grey: 3RT2900-1SB20	• right	0 mm	0 mm	0 mm	0 mm	
housing for side-by-side mountingSnaps onto DIN rail EN 60715 35x7.5/15Snaps onto DIN rail EN 60715 35x7.5/15 <th< td=""><td>Weight, approx.</td><td>0.32 kg</td><td>0.5 kg</td><td>0.8 kg</td><td>2.4 kg</td></th<>	Weight, approx.	0.32 kg	0.5 kg	0.8 kg	2.4 kg	
EN 60715 35x7.5/15EN 60715 35x7.5/15EN 60715 35x7.5/15EN 60715 35x7.5/15Electrical accessoriesBuffer moduleBuffer moduleBuffer moduleBuffer moduleMechanical accessoriesDevice identification label 20 mm × 7 mm, Tl-grey: 3RT2900-1SB20Device identification label 20 mm × 7 mm, Tl-grey: 3RT2900-1SB20		Yes	Yes	Yes	Yes	
Mechanical accessoriesDevice identification label 20 mm × 7 mm, Tl-grey: 3RT2900-1SB20Device identification label 20 mm × 7 mm, Tl-grey: 3RT2900-1SB20	Installation					
20 mm × 7 mm, Tl-grey:         20 mm × 7 mm, Tl-grey:<	Electrical accessories	Buffer module	Buffer module	Buffer module	Buffer module	
MTBF at 40 °C 1 804 044 h 1 998 441 h 1 614 510 h 1 778 916 h	Mechanical accessories	20 mm × 7 mm, TI-grey:				
	MTBF at 40 °C	1 804 044 h	1 998 441 h	1 614 510 h	1 778 916 h	

<sup>1)</sup> Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

# Standard power supplies SITOP smart

l-n	has	6	24	V	D	$\mathbf{c}$
P	Tias	νς,	61			$\mathbf{\overline{\mathbf{v}}}$

Ordering data	Article No.	Accessories	Article No.
SITOP PSU100S 1-phase,	6EP1332-2BA20	SITOP redundancy modules	see page 9/6
24 V DC/2.5 A		SITOP selectivity modules	see page 9/14
Stabilized power supply Input: 120/230 V AC		SITOP buffer modules	see page 9/16
Output: 24 V DC/2.5 A		SITOP DC UPS	see page 8/2
SITOP PSU100S 1-phase, 24 V DC/5 A	6EP1333-2BA20	Device identification label	3RT2900-1SB20
Stabilized power supply Input: 120/230 V AC Output: 24 V DC/5 A		More information	
SITOP PSU100S 1-phase, 24 V DC/10 A	6EP1334-2BA20	TIA Selection Tool:	er supply quickly and easily with th
Stabilized power supply Input: 120/230 V AC Output: 24 V DC / 10 A		http://www.siemens.com/ts	t
SITOP PSU100S 1-phase, 24 V DC/20 A			
Stabilized power supply Input: 120/230 V AC Output: 24 V DC/20 A	6EP1336-2BA10		

### Standard power supplies

SITOP smart

### Overview



The three-phase SITOP smart are the universal and powerful standard power supplies for machinery and plant engineering. Despite their compact design, they offer an excellent overload response: Thanks to a power boost of 150%, loads with high power consumption can be connected without any problems and the permanent overload capability of 120% offers power reserves in case of expansions. The high degree of efficiency results in low energy consumption and minimal heat generation inside the control cabinet.

To further increase 24 V availability, the SITOP smart power supplies can be combined with **buffer**, **DC UPS**, **redundancy** and **selectivity modules**.

#### Main product highlights

- 3-phase, 24 V DC/5 A, 10 A, 20 A and 40 A
- Wide-range input from 340 to 550 V AC for global use
- Compact design no lateral clearances required
- Extra power with 1.5 times the rated current (5 s/min) for brief functional overload
- Permanent overload capability with 1.2 times the rated current up to 45 °C ambient temperature
- Adjustable output voltage for compensating voltage drops
- Signaling contact for easy integration in the plant monitoring system
- Wide temperature range from -25 or 0 to +70 °C
- Comprehensive certifications, such as cULus, cCSAus, ATEX, IECEx and DNV GL

### Technical specifications

Article number	6EP1433-2BA20 <sup>1)</sup>	6EP1434-2BA20 <sup>1)</sup>	6EP1436-2BA10 <sup>1)</sup>	6EP1437-2BA20 <sup>1)</sup>
Product	SITOP PSU300S	SITOP PSU300S	SITOP PSU300S	SITOP PSU300S
Power supply, type	24 V/5 A	24 V/10 A	24 V/20 A	24 V/40 A
Input				
Input	3-phase AC	3-phase AC	3-phase AC	3-phase AC
Rated voltage value Vin rated	400 500 V	400 500 V	400 500 V	400 500 V
Voltage range AC	340 550 V	340 550 V	340 550 V	340 550 V
Wide-range input	Yes	Yes	Yes	Yes
Mains buffering at Iout rated, min.	18 ms; at V <sub>in</sub> = 400 V	7 ms; at V <sub>in</sub> = 400 V	6 ms; at V <sub>in</sub> = 400 V	6 ms; at V <sub>in</sub> = 400 V
Rated line frequency 1	50 Hz	50 Hz	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz	47 63 Hz	47 63 Hz
Input current				
<ul> <li>at rated input voltage 400 V</li> </ul>	0.45 A	0.7 A	1.2 A	2 A
<ul> <li>at rated input voltage 500 V</li> </ul>	0.4 A	0.6 A	1 A	1.7 A
Switch-on current limiting (+25 °C), max.	20 A	20 A	36 A	60 A
l²t, max.	0.5 A <sup>2</sup> ·s	0.5 A <sup>2</sup> ·s	0.9 A <sup>2</sup> ·s	3.4 A <sup>2.</sup> s
Built-in incoming fuse	none	none	none	none
Protection in the mains power input (IEC 898)	Required: 3-pole connected miniature circuit breaker 3 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489-listed, DIVQ)	Required: 3-pole connected miniature circuit breaker 3 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489-listed, DIVQ)	Required: 3-pole connected miniature circuit breaker 3 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489-listed, DIVQ)	Required: 3-pole connected miniature circuit breaker 3 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489-listed, DIVQ)

## Standard power supplies SITOP smart

3-phase, 24 V DC

lechnical specifications (continued)					
Article number	6EP1433-2BA20 <sup>1)</sup>	6EP1434-2BA20 <sup>1)</sup>	6EP1436-2BA10 <sup>1)</sup>	6EP1437-2BA20 <sup>1)</sup>	
Product	SITOP PSU300S	SITOP PSU300S	SITOP PSU300S	SITOP PSU300S	
Power supply, type	24 V/5 A	24 V/10 A	24 V/20 A	24 V/40 A	
Output					
Output	Controlled, isolated DC voltage				
Rated voltage Vout rated DC	24 V	24 V	24 V	24 V	
Total tolerance, static $\pm$	3 %	3 %	3 %	3 %	
Static mains compensation, approx.	0.1 %	0.1 %	0.5 %	1 %	
Static load balancing, approx.	0.1 %	0.15 %	1 %	2 %	
Residual ripple peak-peak, max.	200 mV	200 mV	150 mV	150 mV	
Spikes peak-peak, max. (bandwidth: 20 MHz)	240 mV	240 mV	240 mV	240 mV	
Adjustment range	24 28 V	24 28 V	24 28 V	24 28 V	
Product function Output voltage adjustable	Yes	Yes	Yes	Yes	
Output voltage setting	via potentiometer; max. 120 W	via potentiometer; max. 240 W	via potentiometer; max. 480 W	via potentiometer; max. 960 W	
Status display	Green LED for 24 V OK				
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	
On/off behavior	Overshoot of $V_{\rm out}$ < 5 %	Overshoot of $V_{\rm out} < 5$ %	No overshoot of V <sub>out</sub> (soft start)	No overshoot of V <sub>out</sub> (soft start)	
Startup delay, max.	1.5 s	1.5 s	1.5 s	1.5 s	
Voltage rise, typ.	60 ms	50 ms	30 ms	15 ms	
Voltage increase time of the output voltage maximum	500 ms	500 ms	500 ms	500 ms	
Rated current value Iout rated	5 A	10 A	20 A	40 A	
Current range	0 5 A	0 10 A	0 20 A	0 40 A	
Note	6 A up to +45°C; +60 +70 °C: Derating 5%/K	12 A up to +45°C; +60 +70 °C: Derating 5%/K	24 A up to +45°C; +60 +70 °C: Derating 2%/K	48 A up to +45°C; +60 +70 °C: Derating 3%/K	
Supplied active power typical	120 W	240 W	480 W	960 W	
Short-term overload current					
<ul> <li>on short-circuiting during the start- up typical</li> </ul>	-	-	35 A	65 A	
<ul> <li>at short-circuit during operation typical</li> </ul>	-	-	35 A	65 A	
Duration of overloading capability for excess current	-	-		-	
<ul> <li>on short-circuiting during the start- up</li> </ul>	-	-	100 ms	100 ms	
<ul> <li>at short-circuit during operation</li> </ul>	-	-	100 ms	100 ms	
Parallel switching for enhanced performance	Yes	Yes	Yes	Yes	
Numbers of parallel switchable units for enhanced performance	2	2	2	2	
Efficiency					
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	89.5 %	91 %	91 %	91.5 %	
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	14 W	23 W	47 W	89 W	

# Standard power supplies

SITOP smart

## 3-phase, 24 V DC

Article number	6EP1433-2BA20 <sup>1)</sup>	6EP1434-2BA20 <sup>1)</sup>	6EP1436-2BA10 <sup>1)</sup>	6EP1437-2BA20 <sup>1)</sup>
Product	SITOP PSU300S	SITOP PSU300S	SITOP PSU300S	SITOP PSU300S
Power supply, type	24 V/5 A	24 V/10 A	24 V/20 A	24 V/40 A
Closed-loop control				
Dynamic mains compensation ( <i>V<sub>in rated</sub></i> ±15 %), max.	1 %	1 %	3 %	3 %
Dynamic load smoothing ( <i>I</i> <sub>out</sub> : 50/100/50 %), <i>U</i> <sub>out</sub> ± typ.	1 %	1 %	3 %	1.5 %
Load step setting time 50 to 100%, typ.	3 ms	3 ms	2 ms	1 ms
Load step setting time 100 to 50%, typ.	3 ms	3 ms	2 ms	1 ms
Dynamic load smoothing ( <i>l<sub>out</sub>: 10/90/10 %), U<sub>out</sub> ± typ.</i>	3 %	3 %	3 %	3 %
Load step setting time 10 to 90%, typ.	4 ms	4 ms	2 ms	1 ms
Load step setting time 90 to 10%, typ.	4 ms	4 ms	2 ms	1 ms
Setting time maximum	10 ms	10 ms	10 ms	10 ms
Protection and monitoring				
Output overvoltage protection	protection against overvoltage in case of internal fault $V_{out} < 35$ V	protection against overvoltage in case of internal fault $V_{out} < 35$ V	protection against overvoltage in case of internal fault $V_{out} < 35$ V	protection against overvoltage in case of internal fault V <sub>out</sub> < 35 V
Current limitation, typ.	6.6 A	13 A	25.5 A	50 A
Property of the output Short-circuit proof	Yes	Yes	Yes	Yes
Short-circuit protection	Constant current character- istic	Constant current character- istic	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart
Enduring short circuit current RMS value				
• maximum	8 A	16 A	7 A	14 A
Overcurrent overload capability in normal operation	overload capability 150 % I <sub>out rated</sub> up to 5 s/min	overload capability 150 % I <sub>out rated</sub> up to 5 s/min	overload capability 150 % I <sub>out rated</sub> up to 5 s/min	overload capability 150 % I <sub>out rated</sub> up to 5 s/min
Safety				
Primary/secondary isolation	Yes	Yes	Yes	Yes
Galvanic isolation	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1, transformer acc. to EN 61558-2-16	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1, transformer acc. to EN 61558-2-16	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1, transformer acc. to EN 61558-2-16	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1, transformer acc. to EN 61558-2-16
Protection class	Class I	Class I	Class I	Class I
Leakage current				
• maximum	-	-	3.5 mA	-
typical	-	-	1 mA	-
CE mark	Yes	Yes	Yes	Yes
UL/CUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1 UL 60950-1)
Explosion protection	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cULus Class I Div. 2 (ANSI/ISA-12.12.01-2007, CSA C22.2 No. 213-M1987) Group ABCD, T4	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cULus Class I Div. 2 (ANSI/ISA-12.12.01-2007, CSA C22.2 No. 213-M1987) Group ABCD, T4	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nAC IIC T4 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4	
FM approval	-	-	-	-
CB approval	Yes	Yes	Yes	Yes
Marine approval	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20

Article number	6EP1433-2BA20 <sup>1)</sup>	6EP1434-2BA20 <sup>1)</sup>	6EP1436-2BA10 <sup>1)</sup>	6EP1437-2BA20 <sup>1)</sup>
Product	SITOP PSU300S	SITOP PSU300S	SITOP PSU300S	SITOP PSU300S
Power supply, type	24 V/5 A	24 V/10 A	24 V/20 A	24 V/40 A
EMC				
Emitted interference	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2	EN 61000-3-2	EN 61000-3-2	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data				
Ambient temperature				
<ul> <li>during operation</li> </ul>	-25 +70 °C	-25 +70 °C	-25 +70 °C	-25 +70 °C
- Note	with natural convection	with natural convection	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to	Climate class 3K3,	Climate class 3K3,	Climate class 3K3,	Climate class 3K3,
EN 60721	no condensation	no condensation	no condensation	no condensation
Mechanics				
Connection technology	screw-type terminals	screw-type terminals	screw-type terminals	screw-type terminals
Connections				
<ul> <li>Supply input</li> </ul>	L1, L2, L3, PE: 1 screw terminal each for 0.05 2.5 mm <sup>2</sup> single-core/ finely stranded	L1, L2, L3, PE: 1 screw terminal each for 0.05 2.5 mm <sup>2</sup> single-core/ finely stranded	L1, L2, L3, PE: 1 screw terminal each for 0.5 4 mm <sup>2</sup> single-core/ finely stranded	L1, L2, L3, PE: 1 screw terminal each for 0.5 4 mm <sup>2</sup> single-core/ finely stranded
Output	+, -: 2 screw terminals each for 0.2 2.5 $\mbox{mm}^2$	+, -: 2 screw terminals each for 0.2 2.5 $\mbox{mm}^2$	+, -: 2 screw terminals each for 0.2 4 $mm^2$	+, -: 2 screw terminals ea for 0.5 10 mm <sup>2</sup>
• Auxiliary	13, 14 (alarm signal): 1 screw terminal each for 0.2 2.5 mm <sup>2</sup>	13, 14 (alarm signal): 1 screw terminal each for 0.2 2.5 mm <sup>2</sup>	13, 14 (alarm signal): 1 screw terminal each for 0.05 2.5 mm <sup>2</sup>	13, 14 (alarm signal): 1 screw terminal each for 0.05 2.5 mm <sup>2</sup>
Width of the enclosure	50 mm	70 mm	90 mm	145 mm
Height of the enclosure	125 mm	125 mm	145 mm	145 mm
Depth of the enclosure	120 mm	120 mm	150 mm	150 mm
Required spacing				
• top	-	-	40 mm	40 mm
bottom	-	-	40 mm	40 mm
• left	-	-	0 mm	0 mm
• right	-	-	0 mm	0 mm
Weight, approx.	0.5 kg	0.7 kg	1.6 kg	3.1 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
Electrical accessories	Redundancy module, buffer module, selectivity module, DC UPS	Redundancy module, buffer module, selectivity module, DC UPS	Redundancy module, buffer module, selectivity module, DC UPS	Redundancy module, bu module, selectivity modu DC UPS
Mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey: 3RT2900-1SB20	Device identification label 20 mm × 7 mm, TI-grey: 3RT2900-1SB20	Device identification label 20 mm × 7 mm, TI-grey: 3RT2900-1SB20	Device identification labe 20 mm × 7 mm, TI-grey: 3RT2900-1SB20
MTBF at 40 °C	500 000 h	500 000 h	500 000 h	500 000 h

<sup>1)</sup> Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Siemens KT 10.1 · 2019/2020 3/27

### Standard power supplies

SITOP smart

#### 3-phase, 24 V DC Accessories Ordering data Article No. Article No. SITOP PSU300S 3-phase, 24 V DC/5 A 6EP1433-2BA20 SITOP redundancy modules see page 9/6 SITOP selectivity modules see page 9/14 Stabilized power supply Input: 3 AC 400 ... 500 V Output: 24 V DC/5 A SITOP buffer modules see page 9/16 SITOP DC UPS see page 8/2 SITOP PSU300S 3-phase, 24 V DC/10 A 6EP1434-2BA20 Device identification label 3RT2900-1SB20 Stabilized power supply Input: 3 AC 400 ... 500 V Output: 24 V DC / 10 A More information Select the appropriate power supply quickly and easily with the SITOP PSU300S 3-phase, 6EP1436-2BA10 TIA Selection Tool: 24 V DC/20 A http://www.siemens.com/tst Stabilized power supply Input: 3 AC 400 ... 500 V Output: 24 V DC/20 A SITOP PSU300S 3-phase, 6EP1437-2BA20 24 V DC/40 A Stabilized power supply Input: 3 AC 400 ... 500 V Output: 24 V DC/40 A

© Siemens 2019

# **Basic power supplies**



4/2	Introduction
<b>4/3</b> 4/3 4/4	SITOP lite Introduction 1-phase, 24 V DC
<b>4/8</b> 4/9 4/12 4/15 4/18	LOGO!Power Introduction 1-phase, 5 V DC 1-phase, 12 V DC 1-phase, 15 V DC 1-phase, 24 V DC
<b>4/22</b> 4/22 4/23 4/26	SITOP compact Introduction 1-phase, 12 V DC 1-phase, 24 V DC

### Introduction

### Overview

From flat power supplies for distribution boards through costeffective basic power supplies to slim power supply units for control boxes – SITOP caters to all needs, including in the lower performance range.

LOGO!Power thus offers you mini-power supply units in the LOGO!8 module design. The extremely space-saving SITOP compact devices are ideally suited for distributed applications. And SITOP lite fulfills the main requirements for reliable primary switched-mode regulators at an affordable price.

### Overview

### More information

Select the appropriate power supply quickly and easily with the TIA Selection Tool: http://www.siemens.com/tst



### The low-cost basic power supply

The single-phase SITOP lite power supplies are designed for basic requirements in industrial environments and offer all the key functions at an attractive price. Thanks to the slim design, the power supplies require little space on the standard mounting rail, and their excellent efficiency ensures low thermal losses in the control cabinet.

To further increase 24 V availability, the SITOP lite power supplies can be combined with **DC UPS**, **redundancy** and **selectivity modules**.

### Main product highlights

- 24 V DC/ 2.5 A, 5 A, 10 A and 20 A
- 1-phase wide-range input with manual switchover
- Slim design no lateral installation clearances required
- High degree of efficiency
- Green LED for "24 V OK"
- Adjustable output voltage for compensating voltage drops
- Parallel connection possible
- Ambient temperature range of 0 °C to 60 °C (above 45 °C with derating)
- Short-circuit and overload protection
- · Certification to CE, cULus and CB

SITOP lite

1-phase, 24 V DC

### Overview



The single-phase SITOP lite power supplies are designed for basic requirements in industrial environments and offer all the key functions at an attractive price. Thanks to the slim design, the power supplies require little space on the standard mounting rail, and their excellent efficiency ensures low thermal losses in the control cabinet.

To further increase 24 V availability, the SITOP lite power supplies can be combined with **DC UPS**, **redundancy** and **selectivity modules**.

### Main product highlights

- 24 V DC/ 2.5 A, 5 A, 10 A and 20 A
- 1-phase wide-range input with manual switchover
- Slim design no lateral installation clearances required
- High degree of efficiency
- Green LED for "24 V OK"
- · Adjustable output voltage for compensating voltage drops
- Parallel connection possible
- Ambient temperature range of 0 °C to 60 °C (above 45 °C with derating)
- Short-circuit and overload protection
- Certified according to CE, cULus and CB

·				
Article number	6EP1332-1LB00	6EP1333-1LB00	6EP1334-1LB00	6EP1336-1LB00
Product	SITOP PSU100L	SITOP PSU100L	SITOP PSU100L	SITOP PSU100L
Power supply, type	24 V/2.5 A	24 V/5 A	24 V/10 A	24 V/20 A
Input				
Input	1-phase AC	1-phase AC	1-phase AC	1-phase AC or DC
Rated voltage value Vin rated				100 240 V
Note	Set by means of selector switch on the device	Set by means of selector switch on the device	Set by means of selector switch on the device	-
Supply voltage				
<ul> <li>1 at AC Rated value</li> </ul>	120 V	120 V	120 V	-
<ul> <li>2 at AC Rated value</li> </ul>	230 V	230 V	230 V	-
• at DC	-	-	-	100 240 V
Input voltage				
• 1 at AC	93 132 V	93 132 V	93 132 V	85 264 V
• 2 at AC	187 264 V	187 264 V	187 264 V	-
• at DC	-	-	-	88 370 V
Wide-range input	No	No	No	Yes
Overvoltage resistance	$2.3 \times V_{\text{in rated}}$ , 1.3 ms	$2.3 \times V_{\text{in rated}}$ , 1.3 ms	$2.3 \times V_{\rm in \ rated}$ , 1.3 ms	
Mains buffering at I <sub>out rated</sub> , min.	20 ms; at V <sub>in</sub> = 93/187 V	20 ms; at $V_{\rm in}$ = 93/187 V	20 ms; at V <sub>in</sub> = 93/187 V	20 ms; at $V_{\rm in} = 93/187$ V
Rated line frequency 1	50 Hz	50 Hz	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz	47 63 Hz	47 63 Hz
Input current				
<ul> <li>at rated input voltage 120 V</li> </ul>	1.1 A	2.1 A	4.1 A	5.55 A
<ul> <li>at rated input voltage 230 V</li> </ul>	0.65 A	1.15 A	2 A	2.35 A
Switch-on current limiting (+25 °C), max.	27 A	32 A	65 A	45 A
Duration of inrush current limiting at 25 °C				
typical	3 ms	3 ms	3 ms	15 ms
l²t, max.	0.3 A <sup>2.</sup> s	0.8 A <sup>2.</sup> s	3.3 A <sup>2</sup> ·s	3.3 A <sup>2</sup> ·s
Built-in incoming fuse	T 2 A/250 V (not accessible)	T 3,15 A/250 V (not accessible)	T 6.3 A/250 V (not accessible)	T 10 A/250 V (not accessible)
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 3 A characteristic C	Recommended miniature circuit breaker: from 6 A characteristic C	Recommended miniature circuit breaker: from 10 A characteristic C	Recommended miniature circuit breaker: from 10 A characteristic C

### Technical specifications

Article number	6EP1332-1LB00	6EP1333-1LB00	6EP1334-1LB00	6EP1336-1LB00
Product	SITOP PSU100L	SITOP PSU100L	SITOP PSU100L	SITOP PSU100L
Power supply, type	24 V/2.5 A	24 V/5 A	24 V/10 A	24 V/20 A
Output				
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage Vout DC	24 V	24 V	24 V	24 V
Total tolerance, static ±	3 %	3 %	3 %	3 %
Static mains compensation, approx.	0.1 %	0.1 %	0.1 %	0.1 %
Static load balancing, approx.	0.5 %	0.5 %	0.5 %	1 %
Residual ripple peak-peak, max.	150 mV	150 mV	150 mV	150 mV
Residual ripple peak-peak, typ.	10 mV	50 mV	50 mV	50 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	240 mV	240 mV	240 mV	240 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	50 mV	150 mV	150 mV	100 mV
Adjustment range	22.8 26.4 V	22.8 26.4 V	22.8 26.4 V	22.8 26.4 V
Product function Output voltage adjustable	Yes	Yes	Yes	Yes
Output voltage setting	via potentiometer	via potentiometer	via potentiometer	via potentiometer
Status display	Green LED for 24 V OK	Green LED for 24 V OK	Green LED for 24 V OK	Green LED for 24 V OK
On/off behavior	Overshoot of V <sub>out</sub> approx. 4 %	Overshoot of V <sub>out</sub> approx. 4 %	Overshoot of V <sub>out</sub> approx. 4 %	No overshoot of V <sub>out</sub> (soft start)
Startup delay, max.	1.5 s	1.5 s	1.5 s	1.5 s
Voltage rise, typ.	150 ms	130 ms	170 ms	20 ms
Rated current value Iout rated	2.5 A	5 A	10 A	20 A
Current range	0 2.5 A	0 5 A	0 10 A	0 20 A
Note	+45 +60 °C: Derating 2%/K	+45 +60 °C: Derating 2%/K	+45 +60 °C: Derating 2%/K	+45 +70 °C: Derating 2.5%/K
Supplied active power typical	60 W	120 W	240 W	480 W
Parallel switching for enhanced performance	Yes	Yes	Yes	Yes
Numbers of parallel switchable units for enhanced performance	2	2	2	2
Efficiency				
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	85 %	86 %	89 %	92 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	9 W	17 W	34 W	45 W
Closed-loop control				
Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	0.3 %	0.3 %	0.3 %	0.5 %
Dynamic load smoothing (I <sub>out</sub> : 10/90/10 %), U <sub>out</sub> ± typ.	2 %	2 %	2 %	3 %
Load step setting time 10 to 90%, typ.		0.4 ms	0.5 ms	0.7 ms
Load step setting time 90 to 10%, typ.	0.7 ms	0.4 ms	0.7 ms	6 ms
Protection and monitoring				
Output overvoltage protection	< 33 V	< 33 V	< 33 V	< 33 V
Current limitation, typ.	2.6 A	5.25 A	16 A	24 A
Property of the output Short-circuit proof	Yes	Yes	Yes	Yes
Short-circuit protection	Constant current characteristic	Constant current characteristic	Constant current characteristic	Constant current characteristic
Enduring short circuit current RMS value				
typical	4 A	8 A	12.6 A	24 A
Overload/short-circuit indicator	-	-	-	-

# Basic power supplies SITOP lite

# 1-phase, 24 V DC

Article number	6EP1332-1LB00	6EP1333-1LB00	6EP1334-1LB00	6EP1336-1LB00
Product	SITOP PSU100L	SITOP PSU100L	SITOP PSU100L	SITOP PSU100L
Power supply, type	24 V/2.5 A	24 V/5 A	24 V/10 A	24 V/20 A
Safety				
Primary/secondary isolation	Yes	Yes	Yes	Yes
Galvanic isolation	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178
Protection class	Class I	Class I	Class I	Class I
Leakage current				
• maximum	3.5 mA	3.5 mA	3.5 mA	3.5 mA
• typical	0.4 mA	0.4 mA	0.8 mA	0.8 mA
CE mark	Yes	Yes	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259			
Explosion protection	-	-	-	-
FM approval	-	-	-	-
CB approval	Yes	Yes	Yes	Yes
Marine approval	-	-	-	-
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20
EMC				
Emitted interference	EN 55022 Class A	EN 55022 Class A	EN 55022 Class A	EN 55022 Class B
Supply harmonics limitation	not applicable	-	-	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data				
Ambient temperature				
<ul> <li>during operation</li> </ul>	0 60 °C	0 60 °C	0 60 °C	-25 +70 °C
- Note	with natural convection	with natural convection	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
during storage	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics				
Connection technology	screw-type terminals	screw-type terminals	screw-type terminals	screw-type terminals
Connections				
Supply input	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded
Output	+, -: 2 screw terminals each for 0.5 2.5 $\rm mm^2$	+, -: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup>	+, -: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup>	+, -: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup>
Auxiliary	-	-	-	-
Width of the enclosure	32.5 mm	50 mm	70 mm	110 mm
Height of the enclosure	125 mm	125 mm	125 mm	125 mm
Depth of the enclosure	120 mm	120 mm	120 mm	125 mm
Required spacing				
• top	50 mm	50 mm	50 mm	50 mm
• bottom	50 mm	50 mm	50 mm	50 mm
• left	0 mm	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm	0 mm
Weight, approx.	0.3 kg	0.5 kg	0.75 kg	1.8 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15			
MTBF at 40 °C	3 153 082 h	3 076 166 h	2 333 396 h	
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

# Basic power supplies SITOP lite

Ordering data	Article No.	Accessories		
SITOP PSU100L 1-phase,	6EP1332-1LB00	SITOP redundancy modules	see page 9/6	
24 V DC/2.5 A		SITOP selectivity modules	see page 9/14	
Stabilized power supply Input: 120/230 V AC Output: 24 V DC/2.5 A		SITOP DC UPS	see page 8/2	
SITOP PSU100L 1-phase, 24 V DC/5 A	6EP1333-1LB00			
Stabilized power supply Input: 120/230 VAC Output: 24 V DC/5 A				
SITOP PSU100L 1-phase, 24 V DC/10 A	6EP1334-1LB00			
Stabilized power supply Input: 120/230 V AC Output: 24 V DC / 10 A				
SITOP PSU100L 1-phase, 24 V DC/20 A	6EP1336-1LB00			
Stabilized power supply Input: 100 240 V AC Output: 24 V DC/20 A				

LOGO!Power

### Overview




### The flat power supply unit for distribution boards

### Small. Clever. LOGO!Power

Small. Clever. LOGO!Power: Thanks to its stepped profile design, the LOGO! 8 product line is ideally suited for installation in small distribution boards. The stabilized power supplies with a wide range input of 100 ... 240 V AC ( $85 \dots 264$  V) and 110 ... 300 V DC are available in two performance classes with an output voltage of 5 V and 15 V, in three performance classes with 12 V and in four performance classes with 24 V. The 12 V and 24 V versions are ideal for supplying LOGO! controllers with the corresponding voltage input. The high level of efficiency across the entire load range as well as the low no-load losses result in lower overall energy consumption. Greater convenience when commissioning and servicing thanks to the integrated current monitor. The extended temperature range from -25 °C to +70 °C enables a host of additional applications.

# To further increase 24 V availability, the 24 V LOGO! Power power supply units can be combined with **DC-UPS**, **redundancy** and **selectivity modules**.

LOGO!Power is the ideal choice when components need to be supplied with DC voltage. It can provide currents up to 4 A. This mini power pack can be used regardless of industry, e.g. in building technology applications for light and heating controllers or for access control systems. LOGO!Power is also well-suited for use in industrial automation, such as in packaging machine, machine tool, conveyor belt or sorting system applications.



### **Overview** (continued)

### Main product highlights

- Low width
  - with minimum of 18 mm to maximum of 72 mm, thus requiring very little space in the control cabinet or distribution board
- High energy efficiency with efficiency levels of up to 90% over the entire power range and ERP-compliant no-load losses of < 0.3 W</li>
- Global use due to operating temperature range from -25 °C to +70 °C and international certificates
- Load monitoring due to real-time measurement of the output current without disconnecting the cable, i.e. without interrupting the DC supply
- Flexible mounting with standard rail or wall mounting in different installation positions
- Broad portfolio including 11 devices with 5 V, 12 V, 15 V and 24 V DC up to 100 watts (new: 12 V/0.9 A and 24 V/0.6 A)
- Flexible operation in all standard 1-phase supply networks thanks to wide range input of 100 ... 240 V AC without switchover and operation on DC networks with 110 ... 300 V DC
- Reliability

due to problem-free connection of loads with high inrush currents thanks to power reserve when starting up as well as constant current in the event of overload

### More information

Select the appropriate power supply quickly and easily with the TIA Selection Tool:

http://www.siemens.com/tst

### Basic power supplies LOGO!Power

### Overview



Thanks to its stepped profile design, the LOGO!Power product family is ideally suited for low installation depths, such as in miniature distribution boards. The stabilized power supplies with a wide range input of 100 ... 240 V AC (85 ... 264 V) and 110 ... 300 V DC are available with an output voltage of 5 V in two performance classes. The high level of efficiency across the entire load range as well as the low no-load losses result in lower overall energy consumption. Greater convenience when commissioning and servicing thanks to the integrated current monitor. The extended temperature range from -25 °C to +70 °C enables a host of additional applications.

### Main product highlights

- 5 V DC / 3 A and 6.3 A
- Narrow unit with 36 mm or 54 mm width and overall depth of 53 mm in LOGO! design
- Flexible mounting: Standard rail or wall mounting in a range of installation positions
- Higher energy efficiency: over the entire load range as well as no-load power losses of < 0.3 W</li>
- Integrated current monitor: Actual output current measurement directly at the power supply unit
- Global use: Operating temperature range from -25 °C to +70 °C as well as international certifications such as UL, CSA, FM or ATEX

### Technical specifications

Article number	6EP3310-6SB00-0AY0	6EP3311-6SB00-0AY0
Product	LOGO!Power	LOGO!Power
Power supply, type	5 V/3 A	5 V/6.3 A
Input		
Input	1-phase AC or DC	1-phase AC or DC
Rated voltage value Vin rated	100 240 V	100 240 V
Voltage range AC	85 264 V	85 264 V
Input voltage		
• at DC	110 300 V	110 300 V
Wide-range input	Yes	Yes
Overvoltage resistance	300 V AC for 1 s	300 V AC for 1 s
Mains buffering at Iout rated, min.	40 ms; at <i>V</i> <sub>in</sub> = 187 V	40 ms; at $V_{in} = 187 \text{ V}$
Rated line frequency 1	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz
Input current		
<ul> <li>at rated input voltage 120 V</li> </ul>	0.36 A	0.71 A
<ul> <li>at rated input voltage 230 V</li> </ul>	0.22 A	0.37 A
Switch-on current limiting (+25 °C), max.	26 A	50 A
l²t, max.	0.8 A <sup>2.</sup> s	3 A <sup>2</sup> ·s
Built-in incoming fuse	internal	internal
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 6 A characteristic B or from 2 A characteristic C	Recommended miniature circuit breaker: from 10 A characteristic B or from 6 A characteristic C

# Basic power supplies LOGO!Power

# 1-phase, 5 V DC

Article number	6EP3310-6SB00-0AY0	6EP3311-6SB00-0AY0
Product	LOGO!Power	LOGO!Power
Power supply, type	5 V/3 A	5 V/6.3 A
Output		
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage Vout rated DC	5 V	5 V
Total tolerance, static $\pm$	3 %	3 %
Static mains compensation, approx.	0.1 %	0.1 %
Static load balancing, approx.	0.1 %	0.1 %
Residual ripple peak-peak, max.	100 mV	100 mV
Residual ripple peak-peak, typ.	30 mV	30 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	100 mV	100 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	50 mV	50 mV
Adjustment range	4.6 5.4 V	4.6 5.4 V
Product function Output voltage adjustable	Yes	Yes
Output voltage setting	via potentiometer	via potentiometer
Status display	Green LED for output voltage OK	Green LED for output voltage OK
On/off behavior	No overshoot of V <sub>out</sub> (soft start)	No overshoot of V <sub>out</sub> (soft start)
Startup delay, max.	0.5 s	0.5 s
Voltage rise, typ.	100 ms	100 ms
Rated current value Iout rated	3 A	6.3 A
Current range	0 3 A	0 6.3 A
Note	+55 +70 °C: Derating 2%/K	+55 +70 °C: Derating 2%/K
Supplied active power typical	15 W	31.5 W
Parallel switching for enhanced performance	Yes	Yes
Numbers of parallel switchable units for enhanced performance	2	2
Efficiency		
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	76 %	80 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	5 W	8 W
Power loss [W] during no-load operation maximum	0.3 W	0.3 W
Closed-loop control		
Dynamic mains compensation $(V_{\text{in rated}} \pm 15 \%)$ , max.	0.2 %	0.2 %
Dynamic load smoothing (I <sub>out</sub> : 10/90/10 %), U <sub>out</sub> ± typ.	5 %	7 %
Load step setting time 10 to 90%, typ.		1 ms
Load step setting time 90 to 10%, typ.	1 ms	1 ms
Protection and monitoring		
Output overvoltage protection	Yes, according to EN 60950-1	Yes, according to EN 60950-1
Current limitation, typ.	3.8 A	8.2 A
Property of the output Short-circuit proof	Yes	Yes
Short-circuit protection	Constant current characteristic	Constant current characteristic
Enduring short circuit current RMS value		
• maximum	3.8 A	8.2 A
Overcurrent overload capability in normal operation	overload capability 150% l <sub>out rated</sub> typ. 200 ms	overload capability 150% I <sub>out rated</sub> typ. 200 ms
Overload/short-circuit indicator	-	-
measuring point for output current	50 mV =^ 3 A	50 mV =^ 6.3 A
Overcurrent overload capability when switching on	150% l <sub>out rated</sub> typ. 200 ms	150% I <sub>out rated typ</sub> . 200 ms

# Technical specifications (continued)

Article number	6EP3310-6SB00-0AY0	6EP3311-6SB00-0AY0
Product	LOGO!Power	LOGO!Power
Power supply, type	5 V/3 A	5 V/6.3 A
Safety		
Primary/secondary isolation	Yes	Yes
Galvanic isolation	Safety extra-low output voltage Uout acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage Uout acc. to EN 60950-1 and EN 50178
Protection class	Class II (without protective conductor)	Class II (without protective conductor)
CE mark	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus-Recognized (UL 60950, CSA C22.2 No. 60950), File E151273, NEC class 2 (acc. to UL 1310)	cULus-listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus-recognized (UL 60950, CSA C22.2 No. 60950), File E151273
Explosion protection	ATEX (EX) II 3G Ex nA IIC T3; cULus Class I Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213) Group ABCD, T4, File E488866	ATEX (EX) II 3G Ex nA IIC T3; cULus Class I Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213) Group ABCD, T4, File E488866
FM approval	Class I, Div. 2, Group ABCD, T4	Class I, Div. 2, Group ABCD, T4
CB approval	Yes	Yes
Marine approval	ABS, DNV GL	ABS, DNV GL
Degree of protection (EN 60529)	IP20	IP20
EMC		
Emitted interference	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	not applicable	not applicable
Noise immunity	EN 61000-6-2	EN 61000-6-2
Operating data		
Ambient temperature		
<ul> <li>during operation</li> </ul>	-25 +70 °C	-25 +70 °C
- Note	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics		
Connection technology	screw-type terminals	screw-type terminals
Connections		
Supply input	L, N: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	L, N: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded
Output	+, -: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>	+, -: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>
Auxiliary	-	-
Width of the enclosure	36 mm	54 mm
Height of the enclosure	90 mm	90 mm
Depth of the enclosure	53 mm	53 mm
Required spacing		
• top	20 mm	20 mm
bottom	20 mm	20 mm
• left	0 mm	0 mm
• right	0 mm	0 mm
Weight, approx.	0.12 kg	0.2 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15, direct mounting in different mounting positions	Snaps onto DIN rail EN 60715 35x7.5/15, direct mounting in different mounting positions
MTBF at 40 °C	2 931 709 h	2 654 280 h
Other information	Specifications at rated input voltage and ambient temperature +25 $^\circ\mathrm{C}$ (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

### Ordering data

### LOGO!Power 1-phase, 5 V DC/3 A

Stabilized power supply Input: 100 ... 240 V AC (110 ... 300 V AC) Output: 5 V DC/3 A

### Article No. 6EP3310-6SB00-0AY0

#### LOGO!Power 1-phase, 5 V DC/6.3 A

Stabilized power supply Input: 100 ... 240 V AC (110 ... 300 V AC) Output: 5 V DC/6.3 A Article No.

6EP3311-6SB00-0AY0

4

LOGO!Power

### Overview



Thanks to its stepped profile design, the LOGO!Power product family is ideally suited for low installation depths, such as in miniature distribution boards. The stabilized power supplies with a wide range input of 100 ... 240 V AC ( $85 \dots 264$  V) and 110 ... 300 V DC are available with an output voltage of 12 V in three performance classes. The 12 V versions are ideal for supplying LOGO! controllers with the corresponding voltage input. The high level of efficiency across the entire load range as well as the low no-load losses result in lower overall energy consumption. Greater convenience when commissioning and servicing thanks to integrated current monitor (for devices at least 36 mm wide) The extended temperature range from -25 °C to +70 °C enables a host of additional applications.

#### Main product highlights

- 12 V DC / 0.9 A, 1-9 A and 4.5 A
- Narrow unit with width of 18 mm, 36 mm or 54 mm and overall depth of 53 mm in LOGO! design
- Flexible mounting: Standard rail or wall mounting in a range of installation positions
- Higher energy efficiency: over the entire load range as well as no-load power losses of < 0.3 W</li>
- Integrated current monitor: Actual output current measurement directly at the power supply unit (for devices at least 36 mm wide)
- Global use: Operating temperature range from -25 °C to +70 °C as well as international certifications such as UL, CSA, FM or ATEX

### Technical specifications

		6EB2221 66B00 0AV0	
Article number	6EP3320-6SB00-0AY0	6EP3321-6SB00-0AY0	6EP3322-6SB00-0AY0
Product	LOGO!Power	LOGO!Power	LOGO!Power
Power supply, type	12 V/0.9 A	12 V/1.9 A	12 V/4.5 A
Input			
Input	1-phase AC or DC	1-phase AC or DC	1-phase AC or DC
Rated voltage value Vin rated	100 240 V	100 240 V	100 240 V
Voltage range AC	85 264 V	85 264 V	85 264 V
Input voltage			
• at DC	110 300 V	110 300 V	110 300 V
Wide-range input	Yes	Yes	Yes
Overvoltage resistance	300 V AC for 1 s	300 V AC for 1 s	300 V AC for 1 s
Mains buffering at Iout rated, min.	40 ms; at V <sub>in</sub> = 187 V	40 ms; at V <sub>in</sub> = 187 V	40 ms; at <i>V</i> <sub>in</sub> = 187 V
Rated line frequency 1	50 Hz	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz	47 63 Hz
Input current			
<ul> <li>at rated input voltage 120 V</li> </ul>	0.3 A	0.53 A	1.13 A
<ul> <li>at rated input voltage 230 V</li> </ul>	0.2 A	0.3 A	0.61 A
Switch-on current limiting (+25 °C), max.	20 A	25 A	50 A
l²t, max.	0.8 A <sup>2</sup> ·s	0.8 A <sup>2</sup> ·s	3 A <sup>2</sup> ·s
Built-in incoming fuse	internal	internal	internal
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 6 A characteristic B or from 2 A characteristic C	Recommended miniature circuit breaker: from 6 A characteristic B or from 2 A characteristic C	Recommended miniature circuit breaker: from 10 A characteristic B or from 6 A characteristic C
Output			
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage Vout rated DC	12 V	12 V	12 V
Total tolerance, static ±	3 %	3 %	3 %
Static mains compensation, approx.	0.1 %	0.1 %	0.1 %
Static load balancing, approx.	0.1 %	0.1 %	0.1 %

1-phase, 12 V DC

Article number	6EP3320-6SB00-0AY0	6EP3321-6SB00-0AY0	6EP3322-6SB00-0AY0
Product	LOGO!Power	LOGO!Power	LOGO!Power
Power supply, type	12 V/0.9 A	12 V/1.9 A	12 V/4.5 A
Output (continued)			
Residual ripple peak-peak, max.	200 mV	200 mV	200 mV
Residual ripple peak-peak, typ.	30 mV	30 mV	30 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	300 mV	300 mV	300 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	50 mV	50 mV	50 mV
Adjustment range	-	10.5 16.1 V	10.5 16.1 V
Product function Output voltage adjustable	No	Yes	Yes
Output voltage setting		via potentiometer	via potentiometer
Status display	Green LED for output voltage OK	Green LED for output voltage OK	Green LED for output voltage OK
On/off behavior	No overshoot of Vout (soft start)	No overshoot of Vout (soft start)	No overshoot of Vout (soft start)
Startup delay, max.	0.5 s	0.5 s	0.5 s
Voltage rise, typ.	100 ms	100 ms	100 ms
Rated current value <i>I</i> out rated	0.9 A	1.9 A	4.5 A
Current range	0 0.9 A	0 1.9 A	0 4.5 A
• Note	+55 +70 °C: Derating 2%/K	+55 +70 °C: Derating 2%/K	+55 +70 °C: Derating 2%/K
Supplied active power typical	10.8 W	22.8 W	54 W
Parallel switching for enhanced performance	No	Yes	Yes
Numbers of parallel switchable units for enhanced performance	-	2	2
Efficiency			
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	78 %	81 %	87.1 %
Power loss at <i>V<sub>out rated</sub>, I<sub>out rated</sub>, approx.</i>	3 W	5 W	8 W
Power loss [W] during no-load operation maximum	0.3 W	0.3 W	0.3 W
Closed-loop control			
Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	0.2 %	0.2 %	0.2 %
Dynamic load smoothing ( <i>I<sub>out</sub></i> : 10/90/10 %), <i>U<sub>out</sub> ±</i> typ.	3 %	2 %	4 %
Load step setting time 10 to 90%, typ.	1 ms	1 ms	1 ms
Load step setting time 90 to 10%, typ.	1 ms	1 ms	1 ms
Protection and monitoring			
Output overvoltage protection	Yes, according to EN 60950-1	Yes, according to EN 60950-1	Yes, according to EN 60950-1
Current limitation, typ.	1.3 A	2.5 A	5 A
Property of the output Short-circuit proof	Yes	Yes	Yes
Short-circuit protection Enduring short circuit current	Constant current characteristic	Constant current characteristic	Constant current characteristic
RMS value			
• maximum	1.3 A	2.5 A	5 A
Overcurrent overload capability in normal operation	overload capability 150% <i>l</i> <sub>out rated</sub> typ. 200 ms	overload capability 150% <i>l</i> <sub>out rated</sub> typ. 200 ms	overload capability 150% <i>l</i> <sub>out rated</sub> typ. 200 ms
Overload/short-circuit indicator	-	-	-
measuring point for output current		50 mV =^ 1.9 A	50 mV =^ 4.5 A
Overcurrent overload capability when switching on	150% l <sub>out rated</sub> typ. 200 ms	150% l <sub>out rated</sub> typ. 200 ms	150% l <sub>out rated</sub> typ. 200 ms
Safety	¥	¥	¥
Primary/secondary isolation Galvanic isolation	Yes Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Yes Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Yes Safety extra-low output voltage Uc acc. to EN 60950-1 and EN 50178
Protoction class			
Protection class	Class II (without protective conductor)	Class II (without protective conductor)	Class II (without protective conduction
	Yes	Yes	Yes
UL/CUL (CSA) approval	CULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; CURus-Recog- nized (UL 60950, CSA C22.2 No. 60950), File E151273, NEC class 2	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus-Recog- nized (UL 60950, CSA C22.2 No. 60950), File E151273, NEC class 2	cULus-Listed (UL 508, CSA C22.2 107.1), File E197259; cURus-Reco nized (UL 60950, CSA C22.2 No. 60950), File E151273, NEC class

4/13

LOGO!Power

### 1-phase, 12 V DC

4

### **Technical specifications** (continued)

Article number	6EP3320-6SB00-0AY0	6EP3321-6SB00-0AY0	6EP3322-6SB00-0AY0
Product	LOGO!Power	LOGO!Power	LOGO!Power
Power supply, type	12 V/0.9 A	12 V/1.9 A	12 V/4.5 A
Safety (continued)			
Explosion protection	ATEX (EX) II 3G Ex nA IIC T3; cULus Class I Div. 2 (ANSI/ISA- 12.12.01, CSA C22.2 No. 213) Group ABCD, T4, File E488866	ATEX (EX) II 3G Ex nA IIC T3; cULus Class I Div. 2 (ANSI/ISA- 12.12.01, CSA C22.2 No. 213) Group ABCD, T4, File E488866	ATEX (EX) II 3G Ex nA IIC T3; cULus Class I Div. 2 (ANSI/ISA- 12.12.01, CSA C22.2 No. 213) Group ABCD, T4, File E488866
FM approval	Class I, Div. 2, Group ABCD, T4	Class I, Div. 2, Group ABCD, T4	Class I, Div. 2, Group ABCD, T4
CB approval	Yes	Yes	Yes
Marine approval	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL
Degree of protection (EN 60529)	IP20	IP20	IP20
MC			
Emitted interference	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	not applicable	not applicable	not applicable
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data			
Ambient temperature			
during operation	-25 +70 °C	-25 +70 °C	-25 +70 °C
- Note	with natural convection	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C
during storage	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation
EN 60721			
lechanics			
Connection technology	screw-type terminals	screw-type terminals	screw-type terminals
Connections			
<ul> <li>Supply input</li> </ul>	L, N: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/ finely stranded	L, N: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/ finely stranded	L, N: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/ finely stranded
• Output	+, -: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>	+, -: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>	+, -: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>
Auxiliary	-	-	-
Nidth of the enclosure	18 mm	36 mm	54 mm
Height of the enclosure	90 mm	90 mm	90 mm
Depth of the enclosure	53 mm	53 mm	53 mm
Required spacing			
• top	20 mm	20 mm	20 mm
• bottom	20 mm	20 mm	20 mm
• left	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm
Weight, approx.	0.07 kg	0.12 kg	0.2 kg
Product feature of the enclosure nousing for side-by-side mounting	Yes	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15, direct mounting in different mounting positions	Snaps onto DIN rail EN 60715 35x7.5/15, direct mounting in different mounting positions	Snaps onto DIN rail EN 60715 35x7.5/15, direct mounting in different mounting positions
MTBF at 40 °C	3 793 080 h	2 938 542 h	2 566 680 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
Drdering data	Article No.	Ordering data	Article No.
LOGO!Power 1-phase, 12 V DC/0.9 A	6EP3320-6SB00-0AY0	LOGO!Power 1-phase, 12 V DC/4.5 A	6EP3322-6SB00-0AY0

### Basic power supplies LOGO!Power

### Overview



Thanks to its stepped profile design, the LOGO!Power product family is ideally suited for low installation depths, such as in miniature distribution boards. The stabilized power supplies with a wide range input of 100 ... 240 V AC (85 ... 264 V) and 110 ... 300 V DC are available with an output voltage of 15 V in two performance classes. The high level of efficiency across the entire load range as well as the low no-load losses result in lower overall energy consumption. Greater convenience when commissioning and servicing thanks to the integrated current monitor. The extended temperature range from -25 °C to +70 °C enables a host of additional applications.

#### Main product highlights

- 15 V DC / 1.9 A and 4.0 A
- Narrow unit with 36 mm or 54 mm width and overall depth of 53 mm in LOGO! design
- Flexible mounting: Standard rail or wall mounting in a range of installation positions
- Higher energy efficiency: over the entire load range as well as no-load power losses of < 0.3 W</li>
- Integrated current monitor: Actual output current measurement directly at the power supply unit
- Global use: Operating temperature range from -25 °C to +70 °C as well as international certifications such as UL, CSA, FM or ATEX

### Technical specifications

Article number	6EP3321-6SB10-0AY0	6EP3322-6SB10-0AY0
Product	LOGO!Power	LOGO!Power
Power supply, type	15 V/1.9 A	15 V/4 A
Input		
Input	1-phase AC or DC	1-phase AC or DC
Rated voltage value Vin rated	100 240 V	100 240 V
Voltage range AC	85 264 V	85 264 V
Input voltage		
• at DC	110 300 V	110 300 V
Wide-range input	Yes	Yes
Overvoltage resistance	300 V AC for 1 s	300 V AC for 1 s
Mains buffering at Iout rated, min.	40 ms; at V <sub>in</sub> = 187 V	40 ms; at V <sub>in</sub> = 187 V
Rated line frequency 1	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz
Input current		
<ul> <li>at rated input voltage 120 V</li> </ul>	0.63 A	1.24 A
<ul> <li>at rated input voltage 230 V</li> </ul>	0.33 A	0.68 A
Switch-on current limiting (+25 °C), max.	25 A	55 A
l²t, max.	0.8 A <sup>2</sup> ·s	3 A <sup>2</sup> ·s
Built-in incoming fuse	internal	internal
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 6 A characteristic B or from 2 A characteristic C	Recommended miniature circuit breaker: from 10 A characteristic B or from 6 A characteristic C

# Basic power supplies LOGO!Power

# 1-phase, 15 V DC

Article number	6EP3321-6SB10-0AY0	6EP3322-6SB10-0AY0
Product	LOGO!Power	LOGO!Power
Power supply, type	15 V/1.9 A	15 V/4 A
Output		
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage V <sub>out rated</sub> DC	15 V	15 V
Total tolerance, static $\pm$	3 %	3 %
Static mains compensation, approx.	0.1 %	0.1 %
Static load balancing, approx.	0.1 %	0.1 %
Residual ripple peak-peak, max.	200 mV	200 mV
Residual ripple peak-peak, typ.	30 mV	30 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	300 mV	300 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	50 mV	50 mV
Adjustment range	10.5 16.1 V	10.5 16.1 V
Product function Output voltage adjustable	Yes	Yes
Output voltage setting	via potentiometer	via potentiometer
Status display	Green LED for output voltage OK	Green LED for output voltage OK
On/off behavior	No overshoot of Vout (soft start)	No overshoot of Vout (soft start)
Startup delay, max.	0.5 s	0.5 s
Voltage rise, typ.	100 ms	100 ms
Rated current value Iout rated	1.9 A	4 A
Current range	0 1.9 A	0 4 A
Note	+55 +70 °C: Derating 2%/K	+55 +70 °C: Derating 2%/K
Supplied active power typical	28.5 W	60 W
Parallel switching for enhanced performance	Yes	Yes
Numbers of parallel switchable units for enhanced performance	2	2
Efficiency		
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	83 %	88.4 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	6 W	8 W
Power loss [W] during no-load operation maximum	0.3 W	0.3 W
Closed-loop control		
Dynamic mains compensation ( $V_{in}$ rated ±15 %), max.	0.2 %	0.2 %
Dynamic load smoothing ( <i>I</i> <sub>out</sub> : 10/90/10 %), <i>U</i> <sub>out</sub> ± typ.	2 %	3 %
Load step setting time 10 to 90%, typ.		1 ms
Load step setting time 90 to 10%, typ.	1 ms	1 ms
Protection and monitoring		
Output overvoltage protection	Yes, according to EN 60950-1	Yes, according to EN 60950-1
Current limitation, typ.	2.5 A	5 A
Property of the output Short-circuit proof	Yes	Yes
Short-circuit protection	Constant current characteristic	Constant current characteristic
Enduring short circuit current RMS value		
• maximum	2.5 A	5 A
Overcurrent overload capability in normal operation	overload capability 150% l <sub>out rated</sub> typ. 200 ms	overload capability 150% l <sub>out rated</sub> typ. 200 ms
Overload/short-circuit indicator	-	-
measuring point for output current	50 mV =^ 1.9 A	45 mV =^ 4 A
Overcurrent overload capability when switching on	150% l <sub>out rated</sub> typ. 200 ms	150% / <sub>out rated</sub> typ. 200 ms

Article number	6EP3321-6SB10-0AY0	6EP3322-6SB10-0AY0
Product	LOGO!Power	LOGO!Power
Power supply, type	15 V/1.9 A	15 V/4 A
Safety		
Primary/secondary isolation	Yes	Yes
Galvanic isolation	Safety extra-low output voltage Uout acc. to EN 60950-1 ar	nd EN 50178
Protection class	Class II (without protective conductor)	Class II (without protective conductor)
CE mark	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus-Recognized (UL 60950, CSA C22.2 No. 60950), File E151273, NEC class 2 (acc. to UL 1310)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus-Recognized (UL 60950, CSA C2 No. 60950), File E151273, NEC class 2 (acc. to UL 13
Explosion protection	ATEX (EX) II 3G Ex nA IIC T3; cULus Class I Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213) Group ABCD, T4, File E488866	ATEX (EX) II 3G Ex nA IIC T3; cULus Class I Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213) Group ABCD File E488866
FM approval	Class I, Div. 2, Group ABCD, T4	Class I, Div. 2, Group ABCD, T4
CB approval	Yes	Yes
Marine approval	ABS, BV, DNV GL, LRS	ABS, BV, DNV GL, LRS
Degree of protection (EN 60529)	IP20	IP20
EMC		
Emitted interference	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	not applicable	not applicable
Noise immunity	EN 61000-6-2	EN 61000-6-2
Operating data		
Ambient temperature		
<ul> <li>during operation</li> </ul>	-25 +70 °C	-25 +70 °C
- Note	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics		
Connection technology	screw-type terminals	screw-type terminals
Connections		
<ul> <li>Supply input</li> </ul>	L, N: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/f	finely stranded
Output	+, -: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>	+, -: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>
Auxiliary		-
Width of the enclosure	36 mm	54 mm
Height of the enclosure	90 mm	90 mm
Depth of the enclosure	53 mm	53 mm
Required spacing		
• top	20 mm	20 mm
• bottom	20 mm	20 mm
• left	0 mm	0 mm
• right	0 mm	0 mm
Weight, approx.	0.12 kg	0.2 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15, direct mounting in	n different mounting positions
MTBF at 40 °C	2 938 542 h	2 566 680 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Ordering data	Article No.	Ordering data	Article No.
LOGO!Power 1-phase, 15 V DC/1.9 A	6EP3321-6SB10-0AY0	LOGO!Power 1-phase, 15 V DC/4 A	6EP3322-6SB10-0AY0
Stabilized power supply Input: 100 240 V AC (110 300 V AC) Output: 15 V DC/1.9 A		Stabilized power supply Input: 100 240 V AC (110 300 V AC) Output: 15 V DC/4 A	
		Accessories	

SITOP redundancy modules RED1200

see page 9/6

LOGO!Power

### Overview



Thanks to its stepped profile design, the LOGO!Power product family is ideally suited for low installation depths, such as in miniature distribution boards. The stabilized power supplies with a wide range input of 100 ... 240 V AC ( $85 \dots 264$  V) and 110 ... 300 V DC are available with an output voltage of 24 V in four performance classes. The 24 V versions are ideal for supplying LOGO! controllers with the corresponding voltage input. The high level of efficiency across the entire load range as well as the low no-load losses result in lower overall energy consumption. Greater convenience when commissioning and servicing thanks to integrated current monitor (for devices at least 36 mm wide) The extended temperature range from -25 °C to +70 °C enables a host of additional applications.

To further increase the 24 V availability, the LOGO!Power power supplies can be combined with **DC UPS**, **redundancy** and **selectivity modules**.

### Main product highlights

- 24 V DC / 0.6 A, 1.3 A, 2.5 A and 4.0 A
- Narrow unit with width of 18 mm, 36 mm, 54 mm or 72 mm and overall depth of 53 mm in LOGO! design
- Flexible mounting: Standard rail or wall mounting in a range of installation positions
- Higher energy efficiency: up to 90 % efficiency over the entire load range as well as no-load power losses of < 0.3 W</li>
- Integrated current monitor: Actual output current measurement directly at the power supply unit (for devices at least 36 mm wide)
- Global use: Operating temperature range from -25 °C to +70 °C as well as international certifications such as UL, CSA, FM or ATEX

### Technical specifications

Article number	6EP3330-6SB00-0AY0	6EP3331-6SB00-0AY0	6EP3332-6SB00-0AY0	6EP3333-6SB00-0AY0
Product	LOGO!Power	LOGO!Power	LOGO!Power	LOGO!Power
Power supply, type	24 V/0.6 A	24 V/1.3 A	24 V/2.5 A	24 V/4 A
Input				
Input	1-phase AC or DC	1-phase AC or DC	1-phase AC or DC	1-phase AC or DC
Rated voltage value Vin rated	100 240 V	100 240 V	100 240 V	100 240 V
Voltage range AC	85 264 V	85 264 V	85 264 V	85 264 V
Input voltage				
at DC	110 300 V	110 300 V	110 300 V	110 300 V
Wide-range input	Yes	Yes	Yes	Yes
Overvoltage resistance	300 V AC for 1 s	300 V AC for 1 s	300 V AC for 1 s	300 V AC for 1 s
Mains buffering at Iout rated, min.	40 ms; at V <sub>in</sub> = 187 V	40 ms; at <i>V</i> <sub>in</sub> = 187 V	40 ms; at <i>V</i> <sub>in</sub> = 187 V	40 ms; at V <sub>in</sub> = 187 V
Rated line frequency 1	50 Hz	50 Hz	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz	47 63 Hz	47 63 Hz
Input current				
<ul> <li>at rated input voltage 120 V</li> </ul>	0.3 A	0.7 A	1.22 A	1.95 A
<ul> <li>at rated input voltage 230 V</li> </ul>	0.2 A	0.35 A	0.66 A	0.97 A
Switch-on current limiting (+25 °C), max.	20 A	25 A	52 A	31 A
I²t, max.	0.8 A <sup>2</sup> ·s	0.8 A <sup>2</sup> ·s	3 A <sup>2</sup> ·s	2.5 A <sup>2.</sup> s
Built-in incoming fuse	internal	internal	internal	internal
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 6 A characteristic B or from 2 A characteristic C	Recommended miniature circuit breaker: from 6 A characteristic B or from 2 A characteristic C	Recommended miniature circuit breaker: from 10 A characteristic B or from 6 A characteristic C	Recommended miniature circuit breaker: from 10 A characteristic B o from 6 A characteristic C

1-phase, 24 V DC

Article number	6EP3330-6SB00-0AY0	6EP3331-6SB00-0AY0	6EP3332-6SB00-0AY0	6EP3333-6SB00-0AY0
Product	LOGO!Power	LOGO!Power	LOGO!Power	LOGO!Power
Power supply, type	24 V/0.6 A	24 V/1.3 A	24 V/2.5 A	24 V/4 A
Output				
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage Vout rated DC	24 V	24 V	24 V	24 V
Total tolerance, static ±	3 %	3 %	3 %	3 %
Static mains compensation, approx.	0.1 %	0.1 %	0.1 %	0.1 %
Static load balancing, approx.	0.1 %	0.1 %	0.1 %	0.1 %
Residual ripple peak-peak, max.	200 mV	200 mV	200 mV	200 mV
Residual ripple peak-peak, typ.	30 mV	30 mV	30 mV	30 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	300 mV	300 mV	300 mV	300 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	50 mV	50 mV	50 mV	50 mV
Adjustment range	-	22.2 26.4 V	22.2 26.4 V	22.2 26.4 V
Product function Output voltage adjustable	No	Yes	Yes	Yes
Output voltage setting	-	via potentiometer	via potentiometer	via potentiometer
Status display	Green LED for output voltage OK		Green LED for output voltage OK	
On/off behavior	No overshoot of Vout (soft start)	No overshoot of Vout (soft start)	No overshoot of Vout (soft start)	No overshoot of Vout (soft start)
Startup delay, max.	0.5 s	0.5 s	0.5 s	0.5 s
Voltage rise, typ.	100 ms	100 ms	100 ms	100 ms
Rated current value I <sub>out rated</sub>	0.6 A	1.3 A	2.5 A	4 A
Current range	0 0.6 A	0 1.3 A	0 2.5 A	0 4 A
Note	+55 +70 °C: Derating 2%/K	+55 +70 °C: Derating 2%/K	+55 +70 °C: Derating 2%/K	+55 +70 °C: Derating 2%/K
Supplied active power typical	14.4 W	31.2 W	60 W	96 W
Parallel switching for enhanced performance	No	Yes	Yes	Yes
Numbers of parallel switchable units for enhanced performance	-	2	2	2
Efficiency				
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	81 %	86 %	90 %	89 %
Power loss at <i>V<sub>out rated</sub>, I<sub>out rated</sub>, approx.</i>	3 W	5 W	7 W	12 W
Power loss [W] during no-load operation maximum	0.3 W	0.3 W	0.3 W	0.3 W
Closed-loop control				
Dynamic mains compensation ( <i>V<sub>in rated</sub> ±</i> 15 %), max.	0.2 %	0.2 %	0.2 %	0.2 %
Dynamic load smoothing ( <i>l</i> <sub>out</sub> : 10/90/10 %), <i>U</i> <sub>out</sub> ± typ.	2 %	1 %	2 %	2 %
Load step setting time 10 to 90%, typ.		1 ms	1 ms	1 ms
Load step setting time 90 to 10%, typ.	1 ms	1 ms	1 ms	1 ms
Protection and monitoring	Vee ender t	Man and the state of the state	Man and a second second	Man and a second second
Output overvoltage protection	Yes, according to EN 60950-1	Yes, according to EN 60950-1	Yes, according to EN 60950-1	Yes, according to EN 60950-1
Current limitation, typ. Property of the output Short-circuit	0.8 A Yes	1.7 A Yes	3.2 A Yes	5 A Yes
proof Short-circuit protection	Constant current	Constant current	Constant current characteristic	Constant current characteristic
Enduring short circuit current RMS value	characteristic	characteristic		Characteristic
• maximum	0.8 A	1.7 A	3.2 A	5 A
Overcurrent overload capability in normal operation	overload capability 150% I <sub>out rated</sub> typ. 200 ms	overload capability 150% I <sub>out rated</sub> typ. 200 ms	overload capability 150% I <sub>out rated</sub> typ. 200 ms	overload capability 150 I <sub>out rated</sub> typ. 200 ms
Overload/short-circuit indicator	-	-	-	-
measuring point for output current	-	50 mV =^ 1.3 A	50 mV =^ 2.5 A	50 mV =^ 4 A
Overcurrent overload capability when	150% / typ 200 ms	150% l <sub>out rated</sub> typ. 200 ms	150% lout rated typ. 200 ms	150% / <sub>out rated</sub> typ. 200

Siemens KT 10.1 · 2019/2020

# Basic power supplies LOGO!Power

# 1-phase, 24 V DC

Article number	6EP3330-6SB00-0AY0	6EP3331-6SB00-0AY0	6EP3332-6SB00-0AY0	6EP3333-6SB00-0AY0
Product	LOGO!Power	LOGO!Power	LOGO!Power	LOGO!Power
Power supply, type	24 V/0.6 A	24 V/1.3 A	24 V/2.5 A	24 V/4 A
Safety				
Primary/secondary isolation	Yes	Yes	Yes	Yes
Galvanic isolation	Safety extra-low output voltage <i>U<sub>out</sub></i> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178
Protection class	Class II (without protective conductor)	Class II (without protective conductor)	Class II (without protective conductor)	Class II (without protective conductor)
CE mark	Yes	Yes	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus-Recog- nized (UL 60950, CSA C22.2 No. 60950), File E151273, NEC class 2 (acc. to UL 1310)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus-Recog- nized (UL 60950, CSA C22.2 No. 60950), File E151273, NEC class 2 (acc. to UL 1310)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E 197259; cURus-Recog- nized (UL 60950, CSA C22.2 No. 60950), File E151273, NEC class 2 (acc. to UL 1310)	cULus-listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus-recog- nized (UL 60950, CSA C22.2 No. 60950), File E151273
Explosion protection	ATEX (EX) II 3G Ex nA IIC T3; cULus Class I Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213) Group ABCD, T4, File E488866	ATEX (EX) II 3G Ex nA IIC T3; cULus Class I Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213) Group ABCD, T4, File E488866	ATEX (EX) II 3G Ex nA IIC T3; cULus Class I Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213) Group ABCD, T4, File E488866	ATEX (EX) II 3G Ex nA IIC T3; cULus Class I Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213) Group ABCD, T4, File E488866
FM approval	Class I, Div. 2, Group ABCD, T4	Class I, Div. 2, Group ABCD, T4	Class I, Div. 2, Group ABCD, T4	Class I, Div. 2, Group ABCD, T4
CB approval	Yes	Yes	Yes	Yes
Marine approval	ABS, BV, DNV GL, LRS	ABS, BV, DNV GL, LRS	ABS, BV, DNV GL, LRS	ABS, BV, DNV GL, LRS
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20
EMC				
Emitted interference	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	not applicable	not applicable	not applicable	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data				
Ambient temperature				
<ul> <li>during operation</li> </ul>	-25 +70 °C	-25 +70 °C	-25 +70 °C	-25 +70 °C
- Note	with natural convection	with natural convection	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics				
Connection technology	screw-type terminals	screw-type terminals	screw-type terminals	screw-type terminals
Connections	··· · ···			
Supply input	L, N: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core, finely stranded	L, N: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/ finely stranded	L, N: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core, finely stranded	L, N: 1 screw terminal each / for 0.5 2.5 mm <sup>2</sup> single-core/ finely stranded
Output	+, -: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>	+, -: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>	+, -: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>	+, -: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>
Auxiliary	-	-	-	-
Width of the enclosure	18 mm	36 mm	54 mm	72 mm
Height of the enclosure	90 mm	90 mm	90 mm	90 mm
Depth of the enclosure	53 mm	53 mm	53 mm	53 mm
Required spacing				
• top	20 mm	20 mm	20 mm	20 mm
• bottom	20 mm	20 mm	20 mm	20 mm
• left	0 mm	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm	0 mm
Weight, approx.	0.07 kg	0.12 kg	0.2 kg	0.29 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15, direct mounting in different mounting positions	Snaps onto DIN rail EN 60715 35x7.5/15, direct mounting in different mounting positions	Snaps onto DIN rail EN 60715 35x7.5/15, direct mounting in different mounting positions	Snaps onto DIN rail EN 60715 35x7.5/15, direct mounting in different mounting positions
MTBF at 40 °C	4 415 040 h	3 094 996 h	2 864 520 h	2 391 480 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

# Basic power supplies LOGO!Power

с.	000		24		(m)
	has	17-18	24		

Ordering data	Article No.	Accessories	
LOGO!Power 1-phase, 24 V DC/0.6 A	6EP3330-6SB00-0AY0	SITOP redundancy modules	see page 9/6
		SITOP selectivity modules	see page 9/14
Stabilized power supply Input: 100 240 V AC (110 300 V AC) Output: 24 V DC/0.6 A		SITOP DC UPS	see page 8/2
LOGO!Power 1-phase, 24 V DC/1.3 A	6EP3331-6SB00-0AY0		
Stabilized power supply Input: 100 240 V AC (110 300 V AC) Output: 24 V DC/1.3 A			
LOGO!Power 1-phase, 24 V DC/2.5 A	6EP3332-6SB00-0AY0		
Stabilized power supply Input: 100 240 V AC (110 300 V AC) Output: 24 V DC/2.5 A			
LOGO!Power 1-phase, 24 V DC/4 A	6EP3333-6SB00-0AY0		
Stabilized power supply Input: 100 240 V AC (110 300 V AC) Output: 24 V DC/4 A			

SITOP compact

### Introduction

### Overview



#### The slim power supply unit for control boxes

The single-phase SITOP compact are power supplies for the lower performance range. Thanks to the extremely space-saving slim design, they are especially suited to distributed applications in control boxes or in small control cabinets. The series is characterized by low power losses throughout the entire load range. The losses are extremely low even during idling, which means they are perfectly suited for applications that are frequently in stand-by mode. The SITOP PSU100C power supplies have a wide-range input for AC and DC networks; plug-in terminals facilitate the electrical connection.

To further increase the 24 V availability, the SITOP compact power supplies can be combined with **DC UPS**, **redundancy** and **selectivity modules**.

#### Main product highlights

- 24 V DC/ 0.6 A, 1.3 A, 2.5 A, and 4 A as well as 12 V DC/ 2 A and 6.5 A
- 24 V DC/3.7 A for the supply of NEC class 2 circuits with limited output power (100 VA)
- 1-phase wide-range input from 85 V to 264 V AC or 110 V to 300 V DC
- Small mounting surface thanks to its slim design
- High efficiency across the entire load range: up to 28% energy savings in comparison with similar devices
- Low energy consumption during no-load operation or stand-by: Energy savings of up to 53% are possible
- Adjustable output voltage for compensating voltage drops
- Green LED for "Output voltage OK"
- Plug-in connecting terminals for pre-fabricated wiring and fast electrical connection
- Wide temperature range from –20 to +70 °C
- Comprehensive certifications, such as UL, ATEX or DNV GL

### More information

Select the appropriate power supply quickly and easily with the TIA Selection Tool: http://www.siemens.com/tst

### Basic power supplies SITOP compact

### Overview



The single-phase SITOP compact are power supplies for the lower performance range. Thanks to the extremely space-saving slim design, they are especially suited to distributed applications in control boxes or in small control cabinets. The series is characterized by low power losses throughout the entire load range. The losses are extremely low even during idling, which means they are perfectly suited for applications that are frequently in stand-by mode. The SITOP PSU100C power supplies have a wide-range input for AC and DC networks; plug-in terminals facilitate the electrical connection.

#### Main product highlights

- 12 V DC, 2 A and 6.5 A
- 1-phase wide-range input from 85 V to 264 V AC or 110 V to 300 V DC
- · Small mounting surface thanks to its slim design
- High efficiency across the entire load range.
- Low energy consumption during no-load operation or stand-by
- Adjustable output voltage for compensating voltage drops
  Green LED for "12 V OK"
- Green LED ION 12 V OK
- Plug-in connecting terminals for pre-fabricated wiring and fast electrical connection
- Wide temperature range from -20 to +70 °C
- Comprehensive certifications, such as UL, ATEX or DNV GL

### Technical specifications

Article number	6EP1321-5BA00	6EP1322-5BA10
Product	SITOP PSU100C	SITOP PSU100C
Power supply, type	12 V/2 A	12 V/6.5 A
Input		
Input	1-phase AC or DC	1-phase AC or DC
Rated voltage value Vin rated	100 230 V	100 230 V
Voltage range AC	85 264 V	85 264 V
Input voltage		
• at DC	110 300 V	110 300 V
Wide-range input	Yes	Yes
Overvoltage resistance	$2.3 \times V_{\text{in rated}}$ , 1.3 ms	$2.3 \times V_{\text{in rated}}$ , 1.3 ms
Mains buffering at Iout rated, min.	20 ms; at V <sub>in</sub> = 230 V	20 ms; at <i>V</i> <sub>in</sub> = 230 V
Rated line frequency 1	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz
Input current		
<ul> <li>at rated input voltage 100 V</li> </ul>	0.63 A	1.6 A
<ul> <li>at rated input voltage 230 V</li> </ul>	0.31 A	0.8 A
Switch-on current limiting (+25 °C), max.	33 A	31 A
l²t, max.	1.2 A <sup>2</sup> ·s	3 A <sup>2</sup> ·s
Built-in incoming fuse	internal	internal
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 16 A characteristic B or from 10 A characteristic C	Recommended miniature circuit breaker: from 16 A characteristic B or from 10 A characteristic C

4

# **Basic power supplies** SITOP compact

# 1-phase, 12 V DC

Article number	6EP1321-5BA00	6EP1322-5BA10
Product	SITOP PSU100C	SITOP PSU100C
Power supply, type	12 V/2 A	12 V/6.5 A
Output		
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage Vout rated DC	12 V	12 V
Total tolerance, static $\pm$	3 %	3 %
Static mains compensation, approx.	0.5 %	0.5 %
Static load balancing, approx.	1 %	1 %
Residual ripple peak-peak, max.	200 mV	200 mV
Residual ripple peak-peak, typ.	40 mV	80 mV
Spikes peak-peak, max.	300 mV	300 mV
(bandwidth: 20 MHz)		
Spikes peak-peak, typ. (bandwidth: 20 MHz)	50 mV	80 mV
Adjustment range	10.5 12.9 V	10.5 12.9 V
Product function Output voltage adjustable	Yes	Yes
Output voltage setting	via potentiometer	via potentiometer
Status display	Green LED for output voltage OK	Green LED for output voltage OK
On/off behavior	Overshoot of Vout approx. 5 %	Overshoot of Vout approx. 1 %
Startup delay, max.	0.6 s	1 s
Voltage rise, typ.	10 ms	500 ms
Rated current value Iout rated	2 A	6.5 A
Current range	0 2 A	0 6.5 A
Note	+60 +70 °C: Derating 2%/K; at +70 °C I <sub>out rated</sub> 1.6 A	+55 +70 °C: Derating 1.6%/K; at +70 °C Iout rated 4.9 A
Supplied active power typical	24 W	78 W
Parallel switching for enhanced performance	Yes; Start-up with single nominal load only	Yes; Start-up with single nominal load only
Numbers of parallel switchable units for enhanced performance	2	2
Efficiency		
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	82 %	86 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	5.8 W	12.5 W
Power loss [W] during no-load operation maximum	0.75 W	0.75 W
Closed-loop control		
Dynamic mains compensation ( <i>V</i> <sub>in rated</sub> ±15 %), max.	0.1 %	0.1 %
Dynamic load smoothing $(I_{out}: 10/90/10 \%), U_{out} \pm typ.$	3 %	3 %
Load step setting time 10 to 90%, typ.	4 ms	3 ms
Load step setting time 90 to 10%, typ.		3 ms
Protection and monitoring		
Output overvoltage protection	Yes, according to EN 60950-1	Yes, according to EN 60950-1
Current limitation, typ.	2.4 A	7.2 A
Property of the output Short-circuit	Yes	Yes
proof Short-circuit protection	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart
Overload/short-circuit indicator	-	-
Safety		
Primary/secondary isolation	Yes	Yes
Galvanic isolation	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178
Protection class	Class I	Class I
Leakage current		
• maximum	3.5 mA	3.5 mA
• typical	0.4 mA	0.4 mA
<b>71</b>		

1-phase, 12 V DC

Article number	6EP1321-5BA00	6EP1322-5BA10
Product	SITOP PSU100C	SITOP PSU100C
Power supply, type	12 V/2 A	12 V/6.5 A
Safety (continued)		
CE mark	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-
Explosion protection	IECEx Ex nA IIC T4 Gc; ATEX (EX) II 3G Ex nA IIC T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4	IECEX EX NA IIC T4 GC; ATEX (EX) II 3G EX NA IIC T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class Div. 2, Group ABCD, T4
FM approval	-	-
CB approval	Yes	Yes
Marine approval	ABS, DNV GL	ABS, DNV GL
Degree of protection (EN 60529)	IP20	IP20
EMC		
Emitted interference	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	not applicable	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2
Operating data		
Ambient temperature		
<ul> <li>during operation</li> </ul>	-20 +70 °C	-20 +70 °C
- Note	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics		
Connection technology	screw-type terminals	screw-type terminals
Connections		
Supply input	L, N, PE: Removable screw terminal, each for $1 \ x \ 0.5 \ \ 2.5 \ mm^2$	L, N, PE: Removable screw terminal, each for $1 \times 0.5 \ \ 2.5 \ mm^2$
Output	+: 1 screw terminal for 0.5 2.5 mm <sup>2</sup> ; -: 2 screw terminals for 0.5 2.5 mm <sup>2</sup>	+: 1 screw terminal for 0.5 2.5 mm <sup>2</sup> ; -: 2 screw terminals for 0.5 2.5 mm <sup>2</sup>
Auxiliary	-	-
Width of the enclosure	30 mm	52.5 mm
Height of the enclosure	80 mm	80 mm
Depth of the enclosure	100 mm	100 mm
Required spacing		
• top	50 mm	50 mm
• bottom	50 mm	50 mm
• left	0 mm	0 mm
right	0 mm	0 mm
Weight, approx.	0.12 kg	0.32 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
Electrical accessories	Removable spring-type terminal 6EP1971-5BA00	Removable spring-type terminal 6EP1971-5BA00
MTBF at 40 °C	3 737 060 h	2 853 800 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Ordering data	Article No.	Accessories	Article No.
SITOP PSU100C 1-phase, 12 V DC/2 A	6EP1321-5BA00	SITOP Power PSU100C accessories	6EP1971-5BA00
Stabilized power supply Input:		Removable spring-loaded terminal, 100 units, for SITOP PSU100C	
100 230 V AC (110 300 V DC) Output: 12 V DC/2 A		SITOP redundancy modules RED1200	see page 9/6
SITOP PSU100C 1-phase, 12 V DC/6.5 A	6EP1322-5BA10		
Stabilized power supply Input: 100 230 V AC (110 300 V DC) Output: 12 V DC/6.5 A			

#### **Basic power supplies**

SITOP compact

#### Overview



The single-phase SITOP compact are power supplies for the lower performance range. Thanks to the extremely space-saving slim design, they are especially suited to distributed applications in control boxes or in small control cabinets. The series is characterized by low power losses throughout the entire load range. The losses are extremely low even during idling, which means they are perfectly suited for applications that are frequently in stand-by mode. The SITOP PSU100C power supplies have a wide-range input for AC and DC networks; plug-in terminals facilitate the electrical connection.

#### To further increase the 24 V availability, the SITOP compact power supplies can be combined with **DC UPS**, **redundancy** and **selectivity modules**.

#### Main product highlights

- 24 V DC/ 0.6 A, 1.3 A, 2.5 A and 4 A
- 24 V DC/3.7 A for the supply of NEC class 2 circuits with limited output power (100 VA)
- 1-phase wide-range input from 85 V to 264 V AC or 110 V to 300 V DC
- · Small mounting surface thanks to its slim design
- · High efficiency across the entire load range.
- Low energy consumption during no-load operation or stand-by
- Adjustable output voltage for compensating voltage drops (starting at 1.3 A)
- Green LED for "24 V OK"
- Plug-in connecting terminals for pre-fabricated wiring and fast electrical connection
- Wide temperature range from -20 to +70 °C
- Comprehensive certifications, such as UL, ATEX or DNV GL

Article number	6EP1331-5BA00	6EP1331-5BA10	6EP1332-5BA00	6EP1332-5BA20	6EP1332-5BA10
Product	SITOP PSU100C				
Power supply, type	24 V/0.6 A	24 V/1.3 A	24 V/2.5 A	24 V/3.7 A	24 V/4 A
Input					
Input	1-phase AC or DC				
Rated voltage value $V_{\text{in rated}}$	100 230 V				
Voltage range AC	85 264 V				
Input voltage					
• at DC	110 300 V				
Wide-range input	Yes	Yes	Yes	Yes	Yes
Overvoltage resistance	$2.3 \times V_{\text{in rated}}$ , 1.3 ms				
Mains buffering at Iout rated, min.	20 ms; at V <sub>in</sub> = 230 V	20 ms; at V <sub>in</sub> = 230 V	20 ms; at V <sub>in</sub> = 230 V	20 ms; at V <sub>in</sub> = 230 V	20 ms; at V <sub>in</sub> = 230 V
Rated line frequency 1	50 Hz				
Rated line frequency 2	60 Hz				
Rated line range	47 63 Hz				
Input current					
<ul> <li>at rated input voltage 100 V</li> </ul>	0.28 A	0.63 A	1.21 A	1.88 A	2.25 A
<ul> <li>at rated input voltage 230 V</li> </ul>	0.18 A	0.31 A	0.67 A	0.95 A	1.15 A
Switch-on current limiting (+25 °C), max.	28 A	34 A	31 A	30 A	34 A
l²t, max.	0.7 A <sup>2</sup> ·s	1.2 A <sup>2</sup> ·s	2.4 A <sup>2</sup> ·s	3 A <sup>2</sup> ·s	3 A <sup>2.</sup> s
Built-in incoming fuse	internal	internal	internal	internal	internal
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 16 A characteristic B or from 10 A characteristic C	Recommended miniature circuit breaker: from 16 A characteristic B or from 10 A characteristic C	Recommended miniature circuit breaker: from 16 A characteristic B or from 10 A characteristic C	Recommended miniature circuit breaker: from 16 A characteristic B or from 10 A characteristic C	Recommended miniature circuit breaker: from 16 A characteristic B or from 10 A characteristic C

1-phase, 24 V DC

Article number	6EP1331-5BA00	6EP1331-5BA10	6EP1332-5BA00	6EP1332-5BA20	6EP1332-5BA10
Product	SITOP PSU100C	SITOP PSU100C	SITOP PSU100C	SITOP PSU100C	SITOP PSU100C
Power supply, type	24 V/0.6 A	24 V/1.3 A	24 V/2.5 A	24 V/3.7 A	24 V/4 A
Dutput					
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolate DC voltage
Rated voltage Vout rated DC	24 V	24 V	24 V	24 V	24 V
Total tolerance, static $\pm$	3 %	3 %	3 %	3 %	3 %
Static mains compensation, approx.	0.1 %	0.1 %	0.1 %	0.1 %	0.1 %
Static load balancing, approx.	0.2 %	0.2 %	0.2 %	0.2 %	0.2 %
Residual ripple peak-peak, max.	200 mV	200 mV	200 mV	200 mV	200 mV
Residual ripple peak-peak, typ.	40 mV	25 mV	55 mV	90 mV	80 mV
Spikes peak-peak, max.	300 mV	300 mV	300 mV	300 mV	300 mV
(bandwidth: 20 MHz) Spikes peak-peak, typ.	20 mV	20 mV	50 mV	60 mV	80 mV
(bandwidth: 20 MHz)	20111			00 1110	
Adjustment range	-	22.2 26.4 V	22.2 26.4 V	-	22.2 26.4 V
Product function Output voltage adjustable	No	Yes	Yes	No	Yes
Output voltage setting	-	via potentiometer	via potentiometer	-	via potentiometer
Status display	Green LED for output voltage OK	Green LED for output voltage OK	Green LED for output voltage OK	Green LED for output voltage OK	Green LED for ou voltage OK
On/off behavior	Overshoot of Vout approx. 5 %	Overshoot of Vout approx. 5 %	Overshoot of Vout approx. 1 %	Overshoot of Vout approx. 1 %	Overshoot of Vou approx. 1 %
Startup delay, max.	1 s	0.6 s	0.7 s	1.5 s	1.5 s
Voltage rise, typ.	25 ms	90 ms	100 ms	500 ms	400 ms
Rated current value I <sub>out rated</sub>	0.6 A	1.3 A	2.5 A	3.7 A	4 A
Current range	0 0.6 A	0 1.3 A	0 2.5 A	0 3.7 A	0 4 A
Note		+60 +70 °C: Derating 0.8%/K; at +70 °C / <sub>out rated</sub> 1.2 A	+60 +70 °C: Derating 1.6%/K; at +70 °C / <sub>out rated</sub> 2.1 A	+50 +70 °C: Derating 3.5%/K; at +70 °C / <sub>out rated</sub> 1.1 A	+55 +70 °C: Derating 3%/K; a +70 °C I <sub>out rated</sub> 2
Supplied active power typical Short-term overload current	14 W	30 W	60 W	89 W	96 W
<ul> <li>at short-circuit during operation typical</li> </ul>	1 A	3.1 A	-	-	-
Parallel switching for enhanced performance	No	Yes; Start-up with single nominal load only	Yes; Start-up with single nominal load only	No	Yes; Start-up with single nominal log
Numbers of parallel switchable units for enhanced performance	-	2	2	-	only 2
Efficiency					
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	82 %	86 %	87 %	87 %	88 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	2.6 W	4.5 W	9 W	14 W	13 W
Power loss [W] during no-load operation maximum	0.75 W	0.75 W	0.75 W	0.75 W	0.75 W
Closed-loop control					
Dynamic mains compensation	0.1 %	0.1 %	0.1 %	0.1 %	0.1 %
(V <sub>in rated</sub> ±15 %), max. Dynamic load smoothing	3 %	3 %	3 %	3 %	3 %
( $I_{out}$ : 10/90/10 %), $U_{out} \pm$ typ. Load step setting time 10 to 90%, typ.	3 ms	5 ms	4 ms	4 ms	4 ms
Load step setting time 90 to 10%, typ.	3 ms	5 ms	4 ms	4 ms	4 ms
Protection and monitoring					
Output overvoltage protection	Yes, according to EN 60950-1	Yes, according to EN 60950-1	Yes, according to EN 60950-1	Yes, according to EN 60950-1	Yes, according to EN 60950-1
Current limitation, typ.	0.7 A	1.4 A	3 A	4 A	4.8 A
Property of the output Short-circuit proof	Yes	Yes	Yes	Yes	Yes
Short-circuit protection	Electronic shutdown,	Electronic shutdown,	Electronic shutdown,	Electronic shutdown,	Electronic shutdo

# **Basic power supplies** SITOP compact

# 1-phase, 24 V DC

### Technical specifications (continued)

Article number	6EP1331-5BA00	6EP1331-5BA10	6EP1332-5BA00	6EP1332-5BA20	6EP1332-5BA10
Product	SITOP PSU100C	SITOP PSU100C	SITOP PSU100C	SITOP PSU100C	SITOP PSU100C
Power supply, type	24 V/0.6 A	24 V/1.3 A	24 V/2.5 A	24 V/3.7 A	24 V/4 A
Safety					
Primary/secondary isolation	Yes	Yes	Yes	Yes	Yes
Galvanic isolation	Safety extra-low output voltage <i>U</i> <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage <i>U</i> <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage <i>U</i> <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low outpu voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178
Protection class Leakage current	Class I	Class I	Class I	Class I	Class I
maximum	3.5 mA	3.5 mA	3.5 mA	3.5 mA	3.5 mA
typical	0.4 mA	0.4 mA	0.4 mA	0.4 mA	0.4 mA
CE mark	Yes	Yes	Yes	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus-Recognized (UL 60950, CSA C22.2 No. 60950), File	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus-Recognized (UL 60950, CSA C22.2 No. 60950), File	CULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; CURus-Recognized (UL 60950, CSA C22.2 No. 60950), File E151273, NEC class 2 (acc. to UL 1310)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus-Recognized (UL 60950, CSA C22.2 No. 60950), File	cULus-Listed (UL 508 CSA C22.2 No. 107.1) File E197259; cCSAus (CSA C22.2
Explosion protection	IECEx Ex nA IIC T4 Gc; ATEX (EX) II 3G Ex nA IIC T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4	IECEx Ex nA IIC T4 Gc; ATEX (EX) II 3G Ex nA IIC T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4	IECEx Ex nA IIC T4 Gc; ATEX (EX) II 3G Ex nA IIC T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4	IECEx Ex nA IIC T4 Gc; ATEX (EX) II 3G Ex nA IIC T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4	IECEX EX NA IIC T4 Gc; ATEX (EX) II 3G Ex NA IIC T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4
FM approval	-	-	-	-	-
CB approval	Yes	Yes	Yes	Yes	Yes
Marine approval	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20	IP20
EMC					
Emitted interference	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	not applicable	not applicable	not applicable	EN 61000-3-2	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data					
Ambient temperature					
<ul> <li>during operation</li> </ul>	-20 +70 °C	-20 +70 °C	-20 +70 °C	-20 +70 °C	-20 +70 °C
- Note	with natural convection	with natural convection	with natural convection	with natural convection	with natural convectio
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics					
Connection technology	screw-type terminals	screw-type terminals	screw-type terminals	screw-type terminals	screw-type terminals
Connections					
Supply input	L, N, PE: Removable screw terminal, each for 1 x 0.5 2.5 mm <sup>2</sup>	L, N, PE: Removable screw terminal, each for 1 x 0.5 2.5 mm <sup>2</sup>	L, N, PE: Removable screw terminal, each for 1 x 0.5 2.5 mm <sup>2</sup>	L, N, PE: Removable screw terminal, each for 1 x 0.5 2.5 mm <sup>2</sup>	L, N, PE: Removable screw terminal, each for 1 x 0.5 2.5 mm <sup>2</sup>
	+: 1 screw terminal for	+: 1 screw terminal for	+: 1 screw terminal for	+: 1 screw terminal for	
• Output	0.5 2.5 mm <sup>2</sup> ;	0.5 2.5 mm <sup>2</sup> ;	0.5 2.5 mm <sup>2</sup> ; -: 2 screw terminals for 0.5 2.5 mm <sup>2</sup>	0.5 2.5 mm <sup>2</sup> ; -: 2 screw terminals for 0.5 2.5 mm <sup>2</sup>	0.5 2.5 mm <sup>2</sup> ; -: 2 screw terminals fo 0.5 2.5 mm <sup>2</sup>

1-phase, 24 V DC

Article number	6EP1331-5BA00	6EP1331-5BA10	6EP1332-5BA00	6EP1332-5BA20	6EP1332-5BA10
Product	SITOP PSU100C	SITOP PSU100C	SITOP PSU100C	SITOP PSU100C	SITOP PSU100C
Power supply, type	24 V/0.6 A	24 V/1.3 A	24 V/2.5 A	24 V/3.7 A	24 V/4 A
Mechanics (continued)					
Width of the enclosure	22.5 mm	30 mm	45 mm	52.5 mm	52.5 mm
Height of the enclosure	80 mm	80 mm	80 mm	80 mm	80 mm
Depth of the enclosure	100 mm	100 mm	100 mm	100 mm	100 mm
Required spacing					
• top	50 mm	50 mm	50 mm	50 mm	50 mm
• bottom	50 mm	50 mm	50 mm	50 mm	50 mm
• left	0 mm	0 mm	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm	0 mm	0 mm
Weight, approx.	0.12 kg	0.17 kg	0.22 kg	0.32 kg	0.32 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15			
Electrical accessories	Removable spring- type terminal 6EP1971-5BA00	Removable spring- type terminal 6EP1971-5BA00	Removable spring- type terminal 6EP1971-5BA00	Removable spring- type terminal 6EP1971-5BA00	Removable spring- type terminal 6EP1971-5BA00
MTBF at 40 °C	3 910 833 h	3 838 624 h	2 881 014 h	2 776 544 h	2 726 727 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rat- input voltage and ambient temperature +25 °C (unless otherwise specified)

Ordering data	Article No.	Accessories	Article No.
SITOP PSU100C 1-phase, 24 V DC/0.6 A	6EP1331-5BA00	SITOP redundancy modules	see page 9/6
		SITOP selectivity modules	see page 9/14
Stabilized power supply Input:		SITOP DC UPS	see page 8/2
100 230 V AC (110 300 V DC) Output: 24 V DC/0.6 A		SITOP Power PSU100C accessories	6EP1971-5BA00
SITOP PSU100C 1-phase, 24 V DC/1.3 A	6EP1331-5BA10	Removable spring-loaded terminal, 100 units, for SITOP PSU100C	
Stabilized power supply Input:			
100 230 V AC (110 300 V DC) Output: 24 V DC/1.3 A			
SITOP PSU100C 1-phase, 24 V DC/2.5 A	6EP1332-5BA00		
Stabilized power supply			
Input: 100 230 V AC (110 300 V DC) Output: 24 V DC/2.5 A			
SITOP PSU100C 1-phase, 24 V DC/3.7 A	6EP1332-5BA20		
Stabilized power supply			
Input: 100 230 V AC (110 300 V DC)			
Output: 24 V DC/3.7 A limited output power NEC Class 2			
SITOP PSU100C 1-phase, 24 V DC/4 A	6EP1332-5BA10		
Stabilized power supply			
Input: 100 230 V AC (110 300 V DC)			
Output: 24 V DC/4 A			

# **Basic power supplies**

Notes

© Siemens 2019

### SITOP in the SIMATIC Design



### 5/2 Introduction

- 1-phase, 24 V DC (for S7-300 and ET200M)
- 1-phase, 24 V DC (for S7-1200)
- 5/11 1-phase, 24 V DC
  - (for S7-1500 and ET200MP)
- 5/14 1-phase, 24 V DC (for SIMATIC ET 200SP)
- 5/17 3-phase, 24 V DC (ET200pro PS, IP67)

#### Overview



#### The optimum supply for SIMATIC S7 and more

The original SIMATIC power supplies harmonize perfectly with the PLC network in terms of their design and functionality. This ensures that controller and power supply are perfectly matched. In addition, the startup and power reserves of the power supply units meet the requirements of the respective controllers. The mounting options of both components are the same. The issued certifications and the permitted temperature range allow the components to be used together in almost all areas. The system test that was performed for each of the SITOP power supply units in SIMATIC design together with the respective SIMATIC controller is particularly noteworthy.

In addition to the following SIMATIC systems, the SITOP power supply units in SIMATIC design also supply further consumers reliably with 24 V.

- SIMATIC S7-300
- SIMATIC S7-1200
- SIMATIC S7-1500
- SIMATIC ET 200M
- SIMATIC ET 200MP
- SIMATIC ET 200pro
- SIMATIC ET 200SP

#### More information

Select the appropriate power supply quickly and easily with the TIA Selection Tool: http://www.siemens.com/tst

1-phase, 24 V DC (for S7-300 and ET200M)

#### Overview



The design and functionality of the SIMATIC PS 307 singlephase load power supply (system and load current supply) with automatic range switchover of the input voltage is an optimal match to the SIMATIC S7-300 PLC. By means of the connecting comb that is supplied with the system and load current supply, the supply to the CPU is quickly established. It is also possible to provide a 24 V supply to other S7-300 system components, input/output circuits of the input/output modules and, if necessary, the sensors and actuators. Comprehensive certifications, such as UL, ATEX or GL facilitate universal use (does not apply to outdoor use).

#### Design

- The system and load current supplies are screwed directly onto the S7-300 standard mounting rail and can be mounted directly to the left of the CPU (no installation clearance required)
- Diagnostic LED for indicating "Output voltage 24 V DC OK"
- ON/OFF switches (operation/stand-by) for possible swapping of modules
- Strain-relief assembly for input voltage connection cable

#### Function

- Connection to all 1-phase 50/60 Hz networks (120 / 230 V AC) through automatic range switching (PS307) or manual switching (PS307, outdoor)
- Short-term power failure backup
- Output voltage 24 V DC, stabilized, short circuit-proof, open circuit-proof
- Parallel connection of two power supplies for enhanced performance

Article number	6ES7307-1BA01-0AA0	6ES7305-1BA80-0AA0
Product	PS 307	PS 305 Outdoor
Power supply, type	24 V/2 A	24 V/2 A
Input		
Input	1-phase AC	DC voltage
Note	Automatic range selection	-
Supply voltage		
<ul> <li>1 at AC Rated value</li> </ul>	120 V	-
<ul> <li>2 at AC Rated value</li> </ul>	230 V	-
• at DC		24 110 V
Input voltage		
• 1 at AC	85 132 V	-
• 2 at AC	170 264 V	-
• at DC	-	16.8 138 V
Wide-range input	No	Yes
Overvoltage resistance	$2.3 \times V_{\text{in rated}}$ , 1.3 ms	154 V; 0.1 s
Mains buffering at Iout rated, min.	20 ms; at V <sub>in</sub> = 93/187 V	10 ms; at V <sub>in rated</sub>
Rated line frequency 1	50 Hz	-
Rated line frequency 2	60 Hz	-
Rated line range	47 63 Hz	-
Input current		
<ul> <li>at rated input voltage 120 V</li> </ul>	0.9 A	-
<ul> <li>at rated input voltage 230 V</li> </ul>	0.5 A	-
<ul> <li>at rated input voltage 24 V</li> </ul>	-	2.4 A
<ul> <li>at rated input voltage 110 V</li> </ul>	-	0.6 A
Switch-on current limiting (+25 °C), max.	22 A	20 A

# 1-phase, 24 V DC (for S7-300 and ET200M)

Article number	6ES7307-1BA01-0AA0	6ES7305-1BA80-0AA0
Product	PS 307	PS 305 Outdoor
Power supply, type	24 V/2 A	24 V/2 A
Input (continued)		
Duration of inrush current limiting at 25 °C		
• maximum	3 ms	10 ms
l²t, max.	1 A <sup>2</sup> ·s	5 A <sup>2</sup> ·s
Built-in incoming fuse	T 1.6 A/250 V (not accessible)	T 6.3 A/250 V (not accessible)
•	Recommended miniature circuit breaker: 3 A characteristic C	Recommended miniature circuit breaker: from 10 A characteristic C, suitable for DC
Dutput	S A Characteristic C	HOIT TO A CHARACTERISTIC C, Suitable TO DC
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage V <sub>out</sub> DC	24 V	24 V
Total tolerance, static $\pm$	3 %	3 %
Static mains compensation, approx.	0.1 %	0.2 %
Static load balancing, approx.	0.2 %	0.4 %
Residual ripple peak-peak, max.	50 mV	150 mV
Residual ripple peak-peak, typ.	5 mV	30 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)		240 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	20 mV	150 mV
Product function Output voltage adjustable	No	No
Output voltage setting	-	-
Status display	Green LED for 24 V OK	Green LED for 24 V OK
On/off behavior	No overshoot of V <sub>out</sub> (soft start)	No overshoot of $V_{out}$ (soft start)
Startup delay, max.	2 s	3 s
Voltage rise, typ.	10 ms	5 ms
Rated current value I <sub>out rated</sub>	2 A	2 A
Current range	0 2 A	0 3 A
Note		3 A up to +60°C at $V_{in}$ > 24 V
Supplied active power typical Short-term overload current	48 W	48 W
<ul> <li>on short-circuiting during the start-up typical</li> </ul>	9.Δ	9 A
<ul> <li>at short-circuit during operation typical</li> </ul>	9 A	9 A
Duration of overloading capability for excess current		
<ul> <li>on short-circuiting during the start-up</li> </ul>	90 ms	270 ms
<ul> <li>at short-circuit during operation</li> </ul>	90 ms	270 ms
Parallel switching for enhanced performance	Yes	Yes
Numbers of parallel switchable units for	2	2
enhanced performance	2	2
Efficiency		
Efficiency at V <sub>out rated</sub> , I <sub>out rated,</sub> approx.	84 %	75 %
Power loss at $V_{\text{out rated}}$ , $I_{\text{out rated}}$ , approx.	9 W	16 W
Closed-loop control		
Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	0.1 %	0.3 %
Dynamic load smoothing (I <sub>out</sub> : 50/100/50 %), U <sub>out</sub> ± typ.	0.8 %	2.5 %
Load step setting time 50 to 100%, typ.	0.5 ms	2.5 ms
Load step setting time 100 to 50%, typ.	0.5 ms	2.5 ms
Setting time maximum	1 ms	5 ms
Protection and monitoring		
Output overvoltage protection	Additional control loop, shutdown at < 28.8 V, automatic restart	Additional control loop, shutdown at approx. 30 V automatic restart
Current limitation	2.2 2.6 A	3.3 3.9 A
Property of the output Short-circuit proof	Yes	Yes
Short-circuit protection	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart
Enduring short circuit current RMS value		
• maximum	2 A	2 A
Overload/short-circuit indicator	-	

1-phase, 24 V DC (for S7-300 and ET200M)

Article number	6ES7307-1BA01-0AA0	6ES7305-1BA80-0AA0
Product	PS 307	PS 305 Outdoor
Power supply, type	24 V/2 A	24 V/2 A
Safety		
Primary/secondary isolation	Yes	Yes
Galvanic isolation	Safety extra-low output voltage $V_{out}$ acc. to	Safety extra low output voltage $V_{out}$ according to
	EN 60950-1 and EN 50178	EN 60950-1 and EN 50178, creepage distances a clearances > 5 mm
Protection class	Class I	Class I
Leakage current		
• maximum	3.5 mA	-
• typical	0.5 mA	-
CE mark	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 142), File E143289	UL-Listed (UL 508), File E143289, CSA (CSA C22.2 No. 142)
Explosion protection	ATEX (EX) II 3G Ex nA II T4; cULus (ANSI/ISA 12.12.01, CSA C22.2 No.213) Class I, Div. 2, Group ABCD, T4, File E330455	-
FM approval	Class I, Div. 2, Group ABCD, T4	-
CB approval	No	No
Marine approval	In S7-300 system	-
Degree of protection (EN 60529)	IP20	IP20
EMC		
Emitted interference	EN 55022 Class B	EN 55011 Class A
Supply harmonics limitation	not applicable	not applicable
Noise immunity	EN 61000-6-2	EN 61000-6-2
Operating data		
Ambient temperature		
<ul> <li>during operation</li> </ul>	0 60 °C	-25 +70 °C
- Note	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C
during storage	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K5, transient condensation permitt
Mechanics		
Connection technology	screw-type terminals	screw-type terminals
Connections		
Supply input	L, N, PE: 1 screw terminal each for	L+1, M1, PE: 1 screw terminal each for
	0.5 2.5 mm <sup>2</sup> single-core/finely stranded	0.5 2.5 mm <sup>2</sup> single-core/finely stranded
Output	L+, M: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup>	L+, M: 3 screw terminals each for 0.5 2.5 $\rm mm^2$
Auxiliary		-
Width of the enclosure	40 mm	80 mm
Height of the enclosure	125 mm	125 mm
Depth of the enclosure	120 mm	120 mm
Required spacing		
• top	40 mm	50 mm
• bottom	40 mm	50 mm
• left	0 mm	0 mm
• right	0 mm	0 mm
Weight, approx.	0.4 kg	0.57 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes
Installation	Can be mounted onto S7 rail	Can be mounted onto S7 rail
Mechanical accessories	Mounting adapter for standard mounting rail (6EP1971-1BA00)	Mounting adapter for standard mounting rail (6ES7390-6BA00-0AA0)
MTBF at 40 °C	2 320 078 h	964 506 h

Siemens KT 10.1 · 2019/2020 5/5

### 1-phase, 24 V DC (for S7-300 and ET200M)

Article number	6ES7307-1EA01-0AA0	6ES7307-1EA80-0AA0	6ES7307-1KA02-0AA0
Product	PS 307	PS 307 Outdoor	PS 307
Power supply, type	24 V/5 A	24 V/5 A	24 V/10 A
Input			
Input	1-phase AC	1-phase AC	1-phase AC
Note	Automatic range selection	Set by means of selector switch on the device	Automatic range selection
Supply voltage			
<ul> <li>1 at AC Rated value</li> </ul>	120 V	120 V	120 V
<ul> <li>2 at AC Rated value</li> </ul>	230 V	230 V	230 V
• at DC	-	-	-
Input voltage			
• 1 at AC	85 132 V	93 132 V	85 132 V
• 2 at AC	170 264 V	187 264 V	170 264 V
• at DC	-	-	-
Wide-range input	No	No	No
Overvoltage resistance	$2.3 \times V_{\text{in rated}}$ , 1.3 ms	$2.3 \times V_{\text{in rated}}$ , 1.3 ms	$2.3 \times V_{\text{in rated}}$ , 1.3 ms
Mains buffering at Iout rated, min.	20 ms; at V <sub>in</sub> = 93/187 V	20 ms; at V <sub>in</sub> = 93/187 V	20 ms; at V <sub>in</sub> = 93/187 V
Rated line frequency 1	50 Hz	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz	47 63 Hz
Input current			
at rated input voltage 120 V	2.3 A	2.1 A	4.2 A
at rated input voltage 230 V	1.2 A	1.2 A	1.9 A
<ul> <li>at rated input voltage 24 V</li> </ul>	-	-	-
<ul> <li>at rated input voltage 110 V</li> </ul>	-	-	-
Switch-on current limiting (+25 °C), max.	20 A	45 A	55 A
Duration of inrush current limiting at 25 °C			
• maximum	3 ms	3 ms	3 ms
l²t, max.	1.2 A <sup>2.</sup> s	1.8 A <sup>2.</sup> s	3.3 A <sup>2.</sup> s
Built-in incoming fuse	T 3,15 A/250 V (not accessible)	T 3,15 A/250 V (not accessible)	T 6.3 A/250 V (not accessible)
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 6 A characteristic C	Recommended miniature circuit breaker: from 10 A characteristic C or from 6 A characteristic D	Recommended miniature circuit breaker: from 10 A characteristic C
Output			
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage $V_{out}$ DC	24 V	24 V	24 V
Total tolerance, static $\pm$	3 %	3 %	3%
Static mains compensation, approx.	0.1 %	0.2 %	0.1 %
Static load balancing, approx.	0.5 %	0.4 %	0.5 %
Residual ripple peak-peak, max.	50 mV	150 mV	50 mV
Residual ripple peak-peak, typ.	10 mV	40 mV	15 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)		240 mV	150 mV
Spikes peak-peak, that (bandwidth: 20 MHz) Spikes peak-peak, typ. (bandwidth: 20 MHz)	20 mV	90 mV	60 mV
Product function Output voltage adjustable	No	No	No
Output voltage setting	- Green LED for 24 V OK	- Groop LED for 24 V OK	- Groop LED for 24 V OK
Status display		Green LED for 24 V OK	Green LED for 24 V OK
On/off behavior	No overshoot of V <sub>out</sub> (soft start)	No overshoot of V <sub>out</sub> (soft start)	No overshoot of $V_{out}$ (soft start)
Startup delay, max.	2 s	3 s	2 s
Voltage rise, typ.	10 ms	100 ms	10 ms
Rated current value <i>I</i> <sub>out rated</sub>	5 A	5 A	10 A
Current range	0 5 A	0 5 A	0 10 A
Note			

1-phase, 24 V DC (for S7-300 and ET200M)

Article number	6ES7307-1EA01-0AA0	6ES7307-1EA80-0AA0	6ES7307-1KA02-0AA0
Product	PS 307	PS 307 Outdoor	PS 307
Power supply, type	24 V/5 A	24 V/5 A	24 V/10 A
Output (continued)			
Supplied active power typical	120 W	120 W	240 W
Short-term overload current			
<ul> <li>on short-circuiting during the start-up typica</li> </ul>	20 A	20 A	38 A
<ul> <li>at short-circuit during operation typical</li> </ul>	20 A	20 A	38 A
Duration of overloading capability for excess current			
<ul> <li>on short-circuiting during the start-up</li> </ul>	100 ms	180 ms	80 ms
<ul> <li>at short-circuit during operation</li> </ul>	100 ms	80 ms	80 ms
Parallel switching for enhanced performance Numbers of parallel switchable units for	Yes	No	Yes
enhanced performance			
Efficiency	07 0/	04.9/	00.9/
Efficiency at $V_{\text{out rated}}$ , $I_{\text{out rated}}$ , approx.	87 %	84 %	90 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	18 W	23 W	27 W
Closed-loop control Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	0.1 %	0.3 %	0.1 %
V <sub>in rated</sub> ± 15 %), max. Dynamic load smoothing (I <sub>out</sub> : 50/100/50 %), U <sub>out</sub> ± typ.	1 %	3 %	2 %
Load step setting time 50 to 100%, typ.	0.3 ms	0.2 ms	-
Load step setting time 100 to 50%, typ.	0.3 ms	0.2 ms	-
Setting time maximum		5 ms	0.1 ms
Protection and monitoring		0.110	
Output overvoltage protection	Additional control loop, shutdown at	Additional control loop, shutdown at	Additional control loop shutdow
Current limitation	< 28.8 V, automatic restart 5.5 6.5 A	approx. 30 V, automatic restart 5.5 6.5 A	< 28.8 V, automatic restart 11 12 A
Property of the output Short-circuit proof	Yes	Yes	Yes
Short-circuit protection	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart
Enduring short circuit current RMS value			
• maximum	7 A	5 A	12 A
Overload/short-circuit indicator	-	-	-
Safety			
Primary/secondary isolation	Yes	Yes	Yes
Galvanic isolation	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178	Safety extra low output voltage $V_{out}$ according to EN 60950-1 and EN 50178, creepage distances and clearances > 5 mm	Safety extra-low output voltage acc. to EN 60950-1 and EN 501
Protection class	Class I	Class I	Class I
Leakage current			
• maximum	3.5 mA	3.5 mA	3.5 mA
• typical	0.5 mA	0.3 mA	0.6 mA
CE mark	Yes	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 142), File E143289	UL-Listed (UL 508), File E143289, CSA (CSA C22.2 No. 142)	cULus-Listed (UL 508, CSA C2 No. 142), File E143289
Explosion protection	ATEX (EX) II 3G Ex nA II T4; cULus (ANSI/ISA 12.12.01, CSA C22.2 No.213) Class I, Div. 2, Group ABCD, T4, File E330455		ATEX (EX) II 3G Ex nA II T4; cULus (ANSI/ISA 12.12.01, CSA C22.2 No.213) Class I, Div Group ABCD, T4, File E330455
FM approval	Class I, Div. 2, Group ABCD, T4	-	Class I, Div. 2, Group ABCD, T4
CB approval	No	No	No
Marine approval	In S7-300 system	-	In S7-300 system
Degree of protection (EN 60529)	IP20	IP20	IP20
EMC			
Emitted interference	EN 55022 Class B	EN 55011 Class A	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2	-	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2

# 1-phase, 24 V DC (for S7-300 and ET200M)

Article number	6ES7307-1EA01-0AA0	6ES7307-1EA80-0AA0	6ES7307-1KA02-0AA0
Product	PS 307	PS 307 Outdoor	PS 307
Power supply, type	24 V/5 A	24 V/5 A	24 V/10 A
Operating data			
Ambient temperature			
<ul> <li>during operation</li> </ul>	0 60 °C	-25 +70 °C	0 60 °C
- Note	with natural convection	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K5, transient condensation permitted	Climate class 3K3, no condensation
Mechanics			
Connection technology	screw-type terminals	screw-type terminals	screw-type terminals
Connections			
Supply input	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded
• Output	L+, M: 3 screw terminals each for 0.5 2.5 mm <sup>2</sup>	L+, M: 3 screw terminals each for 0.5 2.5 mm <sup>2</sup>	L+, M: 4 screw terminals each for 0.5 2.5 mm <sup>2</sup>
Auxiliary	-	-	-
Width of the enclosure	60 mm	80 mm	80 mm
Height of the enclosure	125 mm	125 mm	125 mm
Depth of the enclosure	120 mm	120 mm	120 mm
Required spacing			
• top	40 mm	50 mm	40 mm
• bottom	40 mm	50 mm	40 mm
• left	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm
Weight, approx.	0.6 kg	0.57 kg	0.8 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes
Installation	Can be mounted onto S7 rail	Can be mounted onto S7 rail	Can be mounted onto S7 rail
Mechanical accessories	Mounting adapter for standard mounting rail (6EP1971-1BA00)	Mounting adapter for standard mounting rail (6ES7390-6BA00-0AA0)	Mounting adapter for standard mounting rail (6EP1971-1BA00)
MTBF at 40 °C	2 480 589 h	2 231 610 h	1 504 280 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltag and ambient temperature +25 °C (unless otherwise specified)

Ordering data	Article No.	Accessories	Article No.
Load current supply PS 307, 2A	6ES7307-1BA01-0AA0	SIMATIC S7-300 mounting adapter	6EP1971-1BA00
incl. connecting comb Input: 120/230 V AC		For snapping the new PS 307 onto a 35 mm DIN rail (EN 60715)	
Output: 24 V DC/2 A		Spare part	
SIMATIC S7-300 Outdoor, 2A	6ES7305-1BA80-0AA0	SIMATIC S7-300 mounting adapter	6ES7390-6BA00-0AA0
Stabilized power supply PS305 Input: 24 110 V DC Output: 24 V DC/2 A		For snapping the PS307 onto 35 mm DIN rails	
PS 307 load power supply, 5 A	6ES7307-1EA01-0AA0		
incl. connecting comb Input: 120/230 V AC Output: 24 V DC/5 A			
SIMATIC S7-300 Outdoor, 5A	6ES7307-1EA80-0AA0		
Stabilized power supply PS307 Input: 120/230 V AC Output: 24 V DC/5 A			
PS 307 load power supply, 10 A	6ES7307-1KA02-0AA0		
Input: 120/230 V AC Output: 24 V DC/10 A			

#### 1-phase, 24 V DC (for S7-1200)

#### Overview



In terms of design and functionality, the SIMATIC PM 1207 single-phase load power supply (PM = power module) with automatic range selection of the input voltage is an optimal match to the SIMATIC S7-1200 PLC. It provides the supply to CPUs with 24 V input as well as to signal modules, and to 24 V loads connected to the modules. Comprehensive certifications, such as UL, ATEX and DNV GL enable universal use.

#### Design

- The load current supplies are directly fastened to the S7-1200 mounting rail (without connection to the backplane bus) and can be mounted directly to the left of the CPU (no installation clearance required)
- LED for status indicator "24 V OK"
- Two 24 V DC output terminals for connection of 24 V consumers

#### Function

- Connection to all 1-phase networks (120 V AC/230 V AC) through automatic range switching
- Short-term power failure backup
- Parallel connection of two load current supplies for enhanced performance

· · · · · · · · · · · · · · · · · · ·	
Article number	6EP1332-1SH71
Product	S7-1200 PM1207
Power supply, type	24 V/2.5 A
Input	
Input	1-phase AC
Note	Automatic range selection
Supply voltage	
<ul> <li>1 at AC Rated value</li> </ul>	120 V
<ul> <li>2 at AC Rated value</li> </ul>	230 V
Input voltage	
• 1 at AC	85 132 V
• 2 at AC	176 264 V
Wide-range input	No
Overvoltage resistance	$2.3 \times V_{\text{in rated}}$ , 1.3 ms
Mains buffering at Iout rated, min.	20 ms; at V <sub>in</sub> = 93/187 V
Rated line frequency 1	50 Hz
Rated line frequency 2	60 Hz
Rated line range	47 63 Hz
Input current	
<ul> <li>at rated input voltage 120 V</li> </ul>	1.2 A
<ul> <li>at rated input voltage 230 V</li> </ul>	0.67 A
Switch-on current limiting (+25 °C),	13 A
max.	
Duration of inrush current limiting at 25 °C	
• maximum	3 ms
l²t, max.	0.5 A <sup>2</sup> ·s
Built-in incoming fuse	T 3,15 A/250 V (not accessible)
Protection in the mains power input	Recommended miniature circuit
(IEC 898)	breaker: 16 A characteristic B or 10 A characteristic C
Output	
Output	Controlled, isolated DC voltage
Rated voltage Vout DC	24 V
Total tolerance, static $\pm$	3 %
Static mains compensation, approx.	0.1 %
Static load balancing, approx.	0.2 %
Residual ripple peak-peak, max.	150 mV
Spikes peak-peak, max.	240 mV
(bandwidth: 20 MHz)	
Product function Output voltage adjustable	No
Output voltage setting	-
Status display	Green LED for 24 V OK
On/off behavior	No overshoot of $V_{out}$ (soft start)
Startup delay, max.	6 s; 2 s at 230 V, 6 s at 120 V
Voltage rise, typ.	10 ms
Rated current value Iout rated	2.5 A
Current range	0 2.5 A
Supplied active power typical	60 W
Short-term overload current	
<ul> <li>on short-circuiting during the start-up typical</li> </ul>	6 A
• at short-circuit during operation typical	6 A
Duration of overloading capability for excess current	
<ul> <li>on short-circuiting during the start-up</li> </ul>	100 ms
<ul> <li>at short-circuit during operation</li> </ul>	100 ms

### 1-phase, 24 V DC (for S7-1200)

### Technical specifications (continued)

recimical specifications (con	
Article number	6EP1332-1SH71
Product	S7-1200 PM1207
Power supply, type	24 V/2.5 A
Output (continued)	
Parallel switching for enhanced performance	Yes
Numbers of parallel switchable units for enhanced performance	2
Efficiency	
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	83 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	12 W
Closed-loop control	
Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	0.3 %
Dynamic load smoothing ( $I_{out}$ : 50/100/50 %), $U_{out} \pm typ$ .	3 %
Load step setting time 50 to 100%, typ.	5 ms
Load step setting time 100 to 50%, typ.	5 ms
Setting time maximum	5 ms
Protection and monitoring	
Output overvoltage protection	< 33 V
Current limitation, typ.	2.65 A
Property of the output Short-circuit proof	Yes
Short-circuit protection	Constant current characteristic
Enduring short circuit current RMS value	
typical	2.7 A
Overload/short-circuit indicator	-
Safety	
Primary/secondary isolation	Yes
Galvanic isolation	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178
Protection class	Class I
Leakage current	
• maximum	3.5 mA
CE mark	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus-Recognized (UL 60950-1, CSA C22.2 No. 60950-1) File E151273
Explosion protection	ATEX (EX) II 3G Ex nA II T4; cULus (ISA 12.12.01, CSA C22.2 No.213) Class I, Div. 2, Group ABCD, T4, File E330455
FM approval	Class I, Div. 2, Group ABCD, T4
CB approval	Yes
Marine approval Degree of protection (EN 60529)	ABS, BV, DNV GL, LRS, NK IP20

Article number	6EP1332-1SH71	
Product	S7-1200 PM1207	
Power supply, type	24 V/2.5 A	
EMC		
Emitted interference	EN 55022 Class B	
Supply harmonics limitation	not applicable	
Noise immunity	EN 61000-6-2	
Operating data		
Ambient temperature		
<ul> <li>during operation</li> </ul>	-20 60 °C	
- Note	with natural convection	
<ul> <li>during transport</li> </ul>	-40 +85 °C	
<ul> <li>during storage</li> </ul>	-40 +85 °C	
Humidity class according to EN 60721	Climate class 3K3, no condensation	
Mechanics		
Connection technology	screw-type terminals	
Connections		
Supply input	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>	
Output	L+, M: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup>	
Auxiliary	-	
Width of the enclosure	70 mm	
Height of the enclosure	100 mm	
Depth of the enclosure	75 mm	
Required spacing		
• top	20 mm	
• bottom	20 mm	
• left	0 mm	
• right	0 mm	
Weight, approx.	0.3 kg	
Product feature of the enclosure housing for side-by-side mounting	Yes	
Installation	Snaps onto DIN rail EN 60715 35x7.5/15, wall mounting	
MTBF at 40 °C	1 492 537 h	
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	
Ordering data	Article No.	
SIMATIC S7-1200 PM 1207	6EP1332-1SH71	
Input: 120/230 V AC Output: 24 V DC/2.5 A		

5

#### 1-phase, 24 V DC (for S7-1500 and ET200MP)

#### Overview



The design and functionality of the SIMATIC PM 1507 singlephase load power supply (PM = power module) with automatic range selection of the input voltage makes it an optimal match to the SIMATIC S7-1500 PLC. It supplies the S7-1500 system components such as CPU, system power supply (PS), I/O circuits of the input and output modules and, if necessary, the sensors and actuators with 24 V DC.

### Design

- The load current supplies are directly fastened to the S7-1500 mounting rail (without connection to the backplane bus) and can be mounted directly to the left of the CPU (no installation clearance required)
- Diagnostics LEDs to indicate status and faults: Operation, Fault, Stand-by
- ON/OFF switches (operation/stand-by) in case of swapping modules
- Mains connection plug with touch protection and strain relief for connection of input voltage (enables permanent wiring)
- Plug-in 24 V DC output terminal with reverse polarity protection for connection of 24 V loads (enables permanent wiring)

#### Function

- Connection to all 1-phase 50/60 Hz networks (120 / 230 V AC) through automatic range switching
- Short-term mains buffering
- Output voltage of 24 V DC that is limited to maximum 28 V DC (prevents any damages in 24 V loads if input voltage is too high)
- 50% "Extra Power" for 5 seconds per minute for short-term overloads, for example, when switching on 24V consumers

Article number	6EP1332-4BA00	6EP1333-4BA00
Product	S7-1500 PM1507	S7-1500 PM1507
Power supply, type	24 V/3 A	24 V/8 A
Input		
Input	1-phase AC	1-phase AC
Note	Automatic range selection	Automatic range selection
Supply voltage		
<ul> <li>1 at AC Rated value</li> </ul>	120 V	120 V
<ul> <li>2 at AC Rated value</li> </ul>	230 V	230 V
Input voltage		
• 1 at AC	85 132 V	85 132 V
• 2 at AC	170 264 V	170 264 V
Wide-range input	No	No
Overvoltage resistance	$2.3 \times V_{\text{in rated}}$ , 1.3 ms	$2.3 \times V_{\text{in rated}}$ , 1.3 ms
Mains buffering at Iout rated, min.	20 ms; at V <sub>in</sub> = 93/187 V	20 ms; at V <sub>in</sub> = 93/187 V
Rated line frequency 1	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz
Rated line range	45 65 Hz	45 65 Hz
Input current		
<ul> <li>at rated input voltage 120 V</li> </ul>	1.4 A	3.7 A
<ul> <li>at rated input voltage 230 V</li> </ul>	0.8 A	1.7 A
Switch-on current limiting (+25 °C), max.	23 A	62 A
Duration of inrush current limiting at 25 °C		
• maximum	3 ms	3 ms
l²t, max.	1.3 A <sup>2</sup> ·s	12 A <sup>2.</sup> s
Built-in incoming fuse	T 3,15 A/250 V (not accessible)	T 6.3 A/250 V (not accessible)
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: 10 A characteristic B or 6 A characteristic C	Recommended miniature circuit breaker: 16 A characteristic B or 10 A characteristic C

### 1-phase, 24 V DC (for S7-1500 and ET200MP)

### Technical specifications (continued)

recimical specifications (conti		
Article number	6EP1332-4BA00	6EP1333-4BA00
Product	S7-1500 PM1507	S7-1500 PM1507
Power supply, type	24 V/3 A	24 V/8 A
Output		
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage $V_{out}$ DC	24 V	24 V
Total tolerance, static $\pm$	1%	1%
Static mains compensation, approx.	0.1 %	0.1 %
	0.1 %	0.1 %
Static load balancing, approx.	50 mV	50 mV
Residual ripple peak-peak, max.	150 mV	150 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	150 1110	150 1114
Product function Output voltage adjustable	No	No
Status display	LED green for 24 V OK; LED red for error; LED yellow for stand-by	LED green for 24 V OK; LED red for error; LED yellow for stand-by
On/off behavior	No overshoot of $V_{out}$ (soft start)	No overshoot of V <sub>out</sub> (soft start)
Startup delay, max.	1.5 s	1.5 s
Voltage rise, typ.	10 ms	10 ms
Rated current value Iout rated	3 A	8 A
Current range	0 3 A	0 8 A
Supplied active power typical	72 W	192 W
Short-term overload current		
<ul> <li>on short-circuiting during the start-up typical</li> </ul>	12 A	35 A
<ul> <li>at short-circuit during operation typical</li> </ul>	12 A	35 A
Duration of overloading capability for excess current		
<ul> <li>on short-circuiting during the start-up</li> </ul>	70 ms	70 ms
<ul> <li>at short-circuit during operation</li> </ul>	70 ms	70 ms
Parallel switching for enhanced	No	No
performance		
Efficiency		
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	87 %	90 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	11 W	21 W
Closed-loop control		
Dynamic mains compensation ( <i>V</i> <sub>in rated</sub> ±15 %), max.	0.1 %	0.1 %
Dynamic load smoothing (I <sub>out</sub> : 50/100/50 %), U <sub>out</sub> ± typ.	1 %	2 %
Dynamic load smoothing ( <i>I</i> <sub>out</sub> : 10/90/10 %), <i>U</i> <sub>out</sub> ± typ.	3 %	3 %
Load step setting time 10 to 90%, typ.		5 ms
Load step setting time 90 to 10%, typ.		5 ms
Setting time maximum	5 ms	5 ms
Protection and monitoring		
Output overvoltage protection	Additional control loop, limitation (closed loop control) at < 28.8 V	Additional control loop, limitation (closed loop control) at < 28.8 V
Current limitation	3.15 3.6 A	8.4 9.6 A
Current limitation, typ.	3.4 A	9 A
Property of the output Short-circuit proof	Yes	Yes
Short-circuit protection	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart
Overload/short-circuit indicator	-	-
Safety		
Primary/secondary isolation	Yes	Yes
Galvanic isolation	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178 and EN 61131-2	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178 and EN 61131-2
Protection class	Class I	Class I
Leakage current		
• maximum	3.5 mA	3.5 mA
• typical	0.4 mA	1.3 mA

5/12 Siemens KT 10.1 · 2019/2020

1-phase, 24 V DC (for S7-1500 and ET200MP)

Article number	6EP1332-4BA00	6EP1333-4BA00
Product	S7-1500 PM1507	S7-1500 PM1507
Power supply, type	24 V/3 A	24 V/8 A
Safety (continued)		
CE mark	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 142), File E143289	cULus-Listed (UL 508, CSA C22.2 No. 142), File E1432
Explosion protection	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cULus (ANSI/ISA 12.12.01, CSA C22.2 No.213) Class I, Div. 2, Group ABCD, T4, File E330455	IECEX EX NA NC IIC T3 Gc; ATEX (EX) II 3G EX NA NC IIC T3 Gc; cULus (ANSI/ISA 12.12.01, CSA C22.2 No.213) Class I, Div. 2, Group ABCD, T3, File E330455
FM approval	Class I, Div. 2, Group ABCD, T4	Class I, Div. 2, Group ABCD, T4
CB approval	Yes	Yes
Marine approval	ABS, BV, DNV GL	ABS, BV, DNV GL
Degree of protection (EN 60529)	IP20	IP20
EMC		
Emitted interference	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2
Operating data		
Ambient temperature		
during operation	0 60 °C	0 60 °C
- Note	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C
during storage	-40 +85 °C	-40 +85 °C
Humidity class according to	Climate class 3K3, no condensation	Climate class 3K3, no condensation
EN 60721		
Mechanics		
Connection technology	Screw-/spring clamp connection	Screw-/spring clamp connection
Connections		
<ul> <li>Supply input</li> </ul>	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>
Output	L+, M: 2 spring-loaded terminals each for 0.5 to 2.5 mm <sup>2</sup>	L+, M: 2 spring-loaded terminals each for 0.5 to 2.5 mm
Product function		
<ul> <li>removable terminal at input</li> </ul>	Yes	Yes
<ul> <li>removable terminal at output</li> </ul>	Yes	Yes
Width of the enclosure	50 mm	75 mm
Height of the enclosure	147 mm	147 mm
Depth of the enclosure	129 mm	129 mm
Required spacing		
• top	40 mm	40 mm
bottom	40 mm	40 mm
• left	0 mm	0 mm
• right	0 mm	0 mm
Weight, approx.	0.45 kg	0.74 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes
Installation	Can be mounted onto S7-1500 rail	Can be mounted onto S7-1500 rail
MTBF at 40 °C	1 611 993 h	1 362 918 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Ordering data	Article No.	Accessories	
SIMATIC PM 1507	6EP1332-4BA00	Power connector	6ES7590-8AA00-0AA0
Stabilized power supply for SIMATIC S7-1500 Input: 120/230 V AC		With coding element for power supply module; spare part, 10 units per packing unit	
Output: 24 V DC/3 A		Standard mounting rail adapter	6ES7590-6AA00-0AA0
SIMATIC PM 1507 Stabilized power supply for SIMATIC S7-1500 Input: 120/230 V AC Output: 24 V DC/8 A	6EP1333-4BA00	For adapting S7-1500 DIN rails on low or flat standard mounting rails, as pre-assembled in control cabinets and terminal boxes, for example. An adapter must be positioned every 25 cm. Including	
		mounting hardware. 10 units per packing unit	

#### 1-phase, 24 V DC (for SIMATIC ET 200SP)

#### Overview



In terms of design and functionality, the SIMATIC ET 200SP PS single-phase load power supply with automatic range switching of the input voltage is perfectly matched to the SIMATIC ET 200SP. The SIMATIC component and the power supply are wired by means of uniform push-in terminal technology. The 24 V supply provides power to the ET 200SP system components such as the interface module, technology module and communication module, as well as the digital or analog inputs/ outputs. Comprehensive certifications, such as UL or GL, facilitate universal use. Its extremely flat design also makes this power supply ideally suited for installation in compact on-site control boxes.

#### Design

- Mounting of the ET 200SP power supply on DIN rail to the left
   of the SIMATIC ET 200SP component
- Direct mounting side-by-side is possible for the modules; Exception: SIMATIC ET 200SP component has PROFINET connector mounted on the left  $\rightarrow$  5 mm spacer required
- Three separate load circuit connectors for easy commissioning and maintenance
- Diagnostic LED for indicating "Output voltage 24 V DC OK"
- On/off switch for isolated replacement of SIMATIC ET 200SP modules

#### Function

- Connection to all 1-phase 50/60 Hz networks (85 V... 132 V/ 170 V... 264 V) through automatic range switching
- Adjustable output voltage for compensating voltage drops
- Short-term mains buffering
- Signal contact for further processing of "Output voltage 24 V DC OK" in the controller
- Current monitor for further processing of the present energy consumption in the controller
- Output voltage 24 V DC, stabilized, short circuit-proof, open circuit-proof
- Parallel connection of two power supplies for enhanced performance
- High degree of efficiency up to 90%
- Temperature range -30 °C...+60 °C/70 °C with derating
- Easy connection of loads with high power requirements through excellent overload behavior

Article number	6EP7133-6AB00-0BN0	6EP7133-6AE00-0BN0
Product	SIMATIC ET 200SP PS	SIMATIC ET 200SP PS
Power supply, type	24 V/5 A	24 V/10 A
Input		
Input	1-phase AC	1-phase AC
Note	Automatic range selection	Automatic range selection
Supply voltage		
<ul> <li>1 at AC Rated value</li> </ul>	120 V	120 V
<ul> <li>2 at AC Rated value</li> </ul>	230 V	230 V
Input voltage		
• 1 at AC	85 132 V	85 132 V
• 2 at AC	170 264 V	170 264 V
Wide-range input	No	No
Overvoltage resistance	$2.3 \times V_{\text{in rated}}$ , 1.3 ms	$2.3 \times V_{\text{in rated}}$ , 1.3 ms
Mains buffering at I <sub>out rated</sub> , min.	20 ms; at V <sub>in</sub> = 93/187 V	20 ms; at V <sub>in</sub> = 93/187 V
Rated line frequency 1	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz
Input current		
<ul> <li>at rated input voltage 120 V</li> </ul>	2.16 A	4.34 A
<ul> <li>at rated input voltage 230 V</li> </ul>	1.22 A	1.92 A
Switch-on current limiting (+25 °C), max.	45 A	60 A
I²t, max.	3.15 A <sup>2</sup> ·s	6.3 A <sup>2.</sup> s
Built-in incoming fuse	T 3,15 A/250 V (not accessible)	T 6.3 A/250 V (not accessible)
Protection in the mains power input (IEC 898)	recommended LS switch: B/C 6 A/3 A	recommended LS switch: B/C 10 A/6 A

# 1-phase, 24 V DC (for SIMATIC ET 200SP)

Article number	6EP7133-6AB00-0BN0	6EP7133-6AE00-0BN0
Product	SIMATIC ET 200SP PS	SIMATIC ET 200SP PS
Power supply, type	24 V/5 A	24 V/10 A
Output		
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage Vout DC	24 V	24 V
Total tolerance, static ±	3 %	3 %
Static mains compensation, approx.	0.1 %	0.1 %
Static load balancing, approx.	1 %	1 %
Residual ripple peak-peak, max.	150 mV	150 mV
Residual ripple peak-peak, typ.	50 mV	50 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	240 mV	240 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	150 mV	150 mV
Adjustment range	22.8 28 V	22.8 28 V
Product function Output voltage adjustable	Yes	Yes
Output voltage setting	via potentiometer	via potentiometer
Status display	Green LED for 24 V OK	Green LED for 24 V OK
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact, rating 60 V DC/ 0.3 for "24 V OK"
On/off behavior	Overshoot of $V_{out} < 3 \%$	Overshoot of $V_{out}$ < 3 %
Startup delay, max.	0.3 s	0.3 s
Voltage rise, typ.	30 ms	30 ms
Rated current value I <sub>out rated</sub>	5 A	10 A
Current range	0 6 A	0 12 A
Note	5 A up to +60°C; +60 +70 °C: Derating 3%/K	10 A up to +60°C; +60 +70 °C: Derating 3%
Supplied active power typical	120 W	240 W
Short-term overload current		
<ul> <li>on short-circuiting during the start-up typical</li> </ul>	15 A	30 A
<ul> <li>at short-circuit during operation typical</li> </ul>	15 A	30 A
Duration of overloading capability for excess current		
<ul> <li>on short-circuiting during the start-up</li> </ul>	800 ms	750 ms
at short-circuit during operation	800 ms	800 ms
Parallel switching for enhanced performance	Yes	Yes
Numbers of parallel switchable units for enhanced performance	2	2
Efficiency		
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	88 %	90 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	17 W	26 W
Power loss [W] during no-load operation maximum	2.7 W	2.8 W
Closed-loop control		
Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	0.3 %	0.3 %
Dynamic load smoothing ( <i>l<sub>out</sub>: 10/90/10 %), U<sub>out</sub> ±</i> typ.	3 %	3 %
Load step setting time 10 to 90%, typ.	1 ms	1 ms
Load step setting time 90 to 10%, typ.	1 ms	1 ms
Protection and monitoring		
Output overvoltage protection	protection against overvoltage in case of internal fault $V_{\rm out}$ < 31.8 V	protection against overvoltage in case of interr fault $V_{\rm out}$ < 31.8 V
Current limitation	7 7.5 A	14 15 A
Property of the output Short-circuit proof	Yes	Yes
Short-circuit protection	Constant current characteristic	Constant current characteristic
Enduring short circuit current RMS value		
typical	7 A	14.1 A
Overcurrent overload capability in normal operation	overload capability 150 % Iout rated up to 5 s/min	overload capability 150 % Iout rated up to 5 s/mi
Overload/short-circuit indicator	-	-
Safety		
Primary/secondary isolation	Yes	Yes
Galvanic isolation	Safety extra-low output voltage <i>U</i> <sub>out</sub> acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178
	EN 60950-1 and EN 50178	EN 60950-1 and EN 50178

Siemens KT 10.1 · 2019/2020 5/15

### 1-phase, 24 V DC (for SIMATIC ET 200SP)

### **Technical specifications** (continued)

Article number	6EP7133-6AB00-0BN0	6EP7133-6AE00-0BN0
Product	SIMATIC ET 200SP PS	SIMATIC ET 200SP PS
Power supply, type	24 V/5 A	24 V/10 A
Safety (continued)		
Leakage current		
• maximum	3.5 mA	3.5 mA
• typical	1 mA	1 mA
CE mark	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL61010-2-201, CSA C22.2 No.142), cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL61010-2-201, CSA C22.2 No.142), cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
CB approval	Yes	Yes
Marine approval	BV, DNV GL	BV, DNV GL
Degree of protection (EN 60529)	IP20	IP20
EMC		
Emitted interference	EN 61000-6-3 Class B	EN 61000-6-3 Class B
Supply harmonics limitation	EN 61000-3-2	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2
Operating data		
Ambient temperature		
<ul> <li>during operation</li> </ul>	-30 +70 °C	-30 +70 °C
- Note	with natural convection	with natural convection
during transport	-40 +85 °C	-40 +85 °C
during storage	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics		
Connection technology	Push-in terminals	Push-in terminals
Connections		
Supply input	L, N, PE: 1 push-in terminal each for 0.2 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 push-in terminal each for 0.2 2.5 mm <sup>2</sup> single-core/finely stranded
Output	+, -: 2 push-in terminals each for 0.2 2.5 mm <sup>2</sup>	+, -: 2 push-in terminals each for 0.2 2.5 mm <sup>2</sup>
Auxiliary	Signaling contact: 2 push-in terminals for 0.2 2.5 mm <sup>2</sup>	Signaling contact: 2 push-in terminals for 0.2 2.5 mm <sup>2</sup>
Connections signaling contact	2 push-in terminals for 0.2 2.5 mm <sup>2</sup>	2 push-in terminals for 0.2 2.5 mm <sup>2</sup>
Product function		
<ul> <li>removable terminal at input</li> </ul>	Yes	Yes
<ul> <li>removable terminal at output</li> </ul>	Yes	Yes
Width of the enclosure	160 mm	160 mm
Height of the enclosure	117 mm	117 mm
Depth of the enclosure	74 mm	74 mm
Required spacing		
• top	50 mm	50 mm
• bottom	50 mm	50 mm
• left	0 mm	0 mm
• right	0 mm	0 mm
Weight, approx.	0.5 kg	0.7 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
Electrical accessories	Redundancy module, buffer module, selectivity module, DC UPS	Redundancy module, buffer module, selectivity module, DC UPS
MTBF at 40 °C	1 598 441 h	1 114 510 h
Other information	Specifications at rated input voltage and ambient temperature +25 $^{\circ}\mathrm{C}$ (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

#### Ordering data

Article No.

#### 6EP7133-6AB00-0BN0

#### SIMATIC ET 200SP PS

Stabilized power supply for SIMATIC ET 200SP Input: 120/230 V AC Output: 24 V DC/10 A Article No.

#### 6EP7133-6AE00-0BN0

Stabilized power supply for SIMATIC ET 200SP Input: 120/230 V AC Output: 24 V DC/5 A

SIMATIC ET 200SP PS

#### 3-phase, 24 V DC (ET200pro PS, IP67)

### Overview



#### *Power supply for ET200pro:*

• 3-phase, 24 V DC/8 A

The SIMATIC ET200pro PS power supply unit with degree of protection IP67 is used as the electronics/encoder supply and load voltage supply of the new SIMATIC ET 200pro distributed I/O system for use close to the machine without a cabinet. With a signaling contact for "24 V OK" and "Overtemperature", as well as a second plug-in connector for input voltage loop-through.

Article number Product Power supply, type	6ES7148-4PC00-0HA0 SIMATIC ET200pro PS 24 V/8 A
Input	
Input Rated voltage value V <sub>in rated</sub> Voltage range AC	3-phase AC 400 480 V 340 550 V
Note Wide-range input	320 340 V for max. 1 min Yes
Overvoltage resistance Mains buffering at <i>I</i> <sub>out rated</sub> , min. Rated line frequency 1	Implemented internally with variate 15 ms; at $V_{in} = 400 \text{ V}$ 50 Hz
Rated line frequency 2 Rated line range Input current	60 Hz 45 66 Hz
at rated input voltage 400 V Switch-on current limiting (+25 °C), max.	0.5 A 40 A
l²t, max. Built-in incoming fuse	3.5 A <sup>2.</sup> s T 4 A
Protection in the mains power input (IEC 898)	Required: Circuit breaker 3RV2011-1DA10 or 3RV2711-1DD10 (UL 489)
Output	
Output	Controlled, isolated DC voltage
Rated voltage Vout DC	24 V
Total tolerance, static ±	3 %
Static mains compensation, approx.	0.5 %
Static load balancing, approx.	0.5 %
Residual ripple peak-peak, max.	200 mV
Spikes peak-peak, max. (bandwidth: 20 MHz) Product function Output voltage	250 mV
adjustable Output voltage setting	-
Status display	Green LED for 24 V OK
Signaling	max. 30 V, 10 mA; Power-Good (High-Pegel 1L+ for V <sub>out</sub> in range 21.3 29 V); Overtemperature warning at least 30 s before switcl off (high level 1L+ when the max. internal temperature is exceeded)
On/off behavior	Overshoot of $V_{out} < 2 \%$
Startup delay, max.	1.5 s
Voltage rise, typ.	40 ms
Rated current value Iout rated	8 A
Current range	08A
Supplied active power typical Short-term overload current	192 W
<ul> <li>on short-circuiting during the start-up typical</li> <li>at short-circuit during operation</li> </ul>	50 A 50 A
<ul> <li>at short-circuit during operation typical</li> <li>Duration of overloading capability for</li> </ul>	
<ul> <li>excess current</li> <li>on short-circuiting during the start up</li> </ul>	100 ms
start-up <ul> <li>at short-circuit during operation</li> <li>Parallel switching for enhanced</li> </ul>	100 ms No

# 3-phase, 24 V DC (ET200pro PS, IP67)

Technical specifications (con	ntinued)		
Article number	6ES7148-4PC00-0HA0	Article number	6ES7148-4PC00-0HA0
Product	SIMATIC ET200pro PS	Product	SIMATIC ET200pro PS
Power supply, type	24 V/8 A	Power supply, type	24 V/8 A
Efficiency		Mechanics (continued)	
Efficiency at Vout rated, Iout rated,	88 %	Width of the enclosure	310 mm
approx.		Height of the enclosure	135 mm
Power loss at Vout rated, Iout rated,	25 W	Depth of the enclosure	90 mm
approx. Closed-loop control		Weight, approx.	2.8 kg
Dynamic mains compensation	0.5 %	Product feature of the enclosure	No
$(V_{\text{in rated}} \pm 15 \%)$ , max.	0.3 %	housing for side-by-side mounting	
Dynamic load smoothing	1 %	Installation	Can be mounted onto ET200pro mounting rail
( <i>I</i> <sub>out</sub> : 50/100/50 %), <i>U</i> <sub>out</sub> ± typ.		Electrical accessories	Power connector
Setting time maximum	2 ms		(Input: 3RK1911-2BE30 (6 mm <sup>2</sup> ))
Protection and monitoring			(Output: 3RK1911-2BF10 (4 mm <sup>2</sup> ))
Output overvoltage protection	< 33 V	MTBF at 40 °C	196 354 h
Current limitation, typ.	9.4 A	Other information	Specifications at rated input voltage and ambient temperature +25 °C
Property of the output Short-circuit proof	Yes		(unless otherwise specified)
Short-circuit protection	Electronic shutdown,		
	automatic restart	Ordering data	Article No.
Enduring short circuit current			Al licle No.
RMS value	10.1	SIMATIC ET 200pro PS	6ES7148-4PC00-0HA0
• maximum	10 A	Stabilized power supply in	
Overload/short-circuit indicator	-	distributed I/O system design,	
Safety	N .	permitting the loop-through of energy to further modules; with	
Primary/secondary isolation	Yes	degree of protection IP67;	
Galvanic isolation	Protective extra low output voltage $V_{out}$ according to EN 60950-1 and	Input: 400-480 V 3 AC Output: 24 V DC/8 A	
	EN 50178		
Protection class	Class I		
Leakage current		Accessories	Article No.
• maximum	3.5 mA	Power connector	
<ul> <li>typical</li> </ul>	0.4 mA		
CE mark	Yes	For connecting to the distributed I/O system	
UL/cUL (CSA) approval	UL-Listed (UL 508) according to NFPA compatibility (National Fire	• For X1 (6 mm <sup>2</sup> )	3RK1911-2BE30
	Protection Association),	• For X2 (4 mm <sup>2</sup> )	3RK1911-2BF10
	see operating instructions	National Fire Protection	
Explosion protection	-	Association compatible	
FM approval	-	These devices are only approved for installation in	
CB approval	Yes	industrial machinery according to	
Marine approval	-	the NFPA79 Electrical Standard for	
Degree of protection (EN 60529)	IP67, enclosure type 5 indoor	Industrial Machinery. • for X1 SIMATIC ET200pro PS	
EMC		61 88 201 1003.xx (AWG10)*	* https://www.harting.com
Emitted interference	EN 55022 Class A	• for X1 SITOP PSU300P	
Supply harmonics limitation	- EN 01000 C 0	61 88 201 1000.xx / 61 88 201 1002.xx (AWG14)*	
Noise immunity	EN 61000-6-2	<ul> <li>for X2 SIMATIC ET200pro PS</li> </ul>	
Operating data		61 88 202 1010.xx (AWG10)*	
Ambient temperature	-25 +55 °C	supplied blanking cap for X2	3RK1902-0CK00
<ul> <li>during operation</li> <li>Note</li> </ul>	-25 +55 °C with natural convection	<ul> <li>for X3 Phoenix-Contact</li> </ul>	
during transport	-40 +70 °C	SAC-5P-M12-M12FS	
during storage	-40 +70 °C	supplied blanking cap for X3	
Humidity class according to	Climate class 3K3, no condensation	Sealing cap	
EN 60721		For 9-pole power sockets	
Mechanics		• X2 (1 unit)	3RK1902-0CK00
Connection technology	screw-type terminals	• X2 (10 units)	3RK1902-0CJ00
Connections			
Supply input	L1, L2, L3, PE: Plug connector HAN Q4/2 (counterpart see "Electrical accessories")		
• Output	L+, M: 2 x 1.5 mm <sup>2</sup> each (4-pole cable for +/- with open, labeled		
	ends, 4 x 1.5 mm <sup>2</sup> )		
• Auxiliary	Alarm signals: M12 plug-in connector 5-pin		

5/18 Siemens KT 10.1 · 2019/2020

© Siemens 2019

### **DC/DC** converter



6/2	Overview
6/3	SITOP PSU3400
6/10	SITOP PSU400M
6/12	Other DC/DC converters
6/12	48–220 V DC/24 V DC/0.375 A
6/14	48-110 V DC/24 V DC/2 A
6/16	24 V DC/12 V DC/2.5 A
6/18	48 V DC/24 V DC/5 A

6

#### Introduction

#### Overview



# SITOP DC-DC converters – for a stable power supply supply, even with input voltage fluctuations

On the one hand, a DC-DC converter can be used as a "refresher": when long distances are bridged, this module ensures reliable voltage supply to the remote load.

On the other hand, this module serves to stabilize the power supply in the downstream branch case of an unstable supply infeed.

DC-DC converters are particularly suitable for use in batterypowered applications. The output voltage of the battery varies, depending on the state of charge. A DC-DC converter ensures a stable 24 V DC supply of connected loads, such as control units (CPUs).

#### Overview



#### SITOP PSU3400 DC-DC converter – ensures a stable 12 V, 24 V or 48 V supply, even with input voltage fluctuations

DC-DC converters transform DC voltage supplied at the input into DC voltage with a higher, equal or lower voltage level. This module is particularly suitable for using with battery-operated devices. The output voltage of the battery varies depending on the state of charge. DC/DC converters ensure a stable 12 V DC or 24 V DC supply from connected loads, such as control units (CPUs). If the power supply is unstable, these modules also serve to stabilize the voltage supply in the downstream branch.

The benefits at a glance

- Wide input voltage range—optimized for operation with 24 V DC and 48 V DC batteries (for all states of charge)
- Reverse polarity protection at the input
- Regulated DC output voltage for reliable supply of connected loads
- · Adjustable output voltage for compensation of voltage drops
- Slim design: 32 mm width
- Permanent overload capability with 1.2 times the rated current up to 40 °C ambient temperature
- High efficiency of 89%-93%
- Minimal no-load losses of max. 1.5 W
- Ambient temperature range from -25 to +70 °C (derating > 60 °C)
- LED display for easy recognition of operating state
- Overvoltage protection on input side through insulation voltage input/output 1.5 kV DC
- CE marking and cULus approval
- Approvals for DNV GL, ABS (available soon)
- Parallel switching for enhanced performance

### SITOP PSU3400

Article number		6EP3233-0TA00-0AY0			
Product	SITOP PSU3400				
Power supply, type	24 V/5 A	24 V/5 A	12 V/8 A	24 V/3.5 A	24 V/4 A
Input					
Input	DC voltage				
Supply voltage					
• at DC	24 24 V	48 48 V	24 24 V	48 48 V	12 12 V
Input voltage					
• at DC	14 32 V	28 60 V	14 32 V	28 60 V	9 18 V
Note	Startup as of 18 V, derating necessary for 14 18 V DC	Startup as of 36 V, derating necessary for 28 36 V DC	Startup as of 18 V, derating necessary for 14 18 V DC	Startup as of 36 V, derating necessary for 28 36 V DC	-
Wide-range input	No	No	No	No	No
Overvoltage resistance	-	-	-	-	-
Mains buffering at I <sub>out rated</sub> , min.	5 ms; at $V_{in}$ = 24 V	5 ms; at $V_{in}$ = 48 V	5 ms; at $V_{in}$ = 24 V	5 ms; at $V_{in}$ = 48 V	2 ms; at $V_{in}$ = 12 V
Input current					
<ul> <li>at rated input voltage 24 V</li> </ul>	5.5 A	-	4.5 A	-	9 A
<ul> <li>at rated input voltage 48 V</li> </ul>	-	2.7 A	-	1.9 A	-
Switch-on current limiting (+25 °C), max.	15 A				
l²t, max.	0.18 A <sup>2.</sup> s	0.12 A <sup>2</sup> ·s	0.18 A <sup>2</sup> ·s	0.09 A <sup>2</sup> ·s	0.08 A <sup>2.</sup> s
Built-in incoming fuse	25 A (not accessible), breaking capacity 300 A	15 A (not accessible), breaking capacity 100 A	15 A (not accessible), breaking capacity 100 A	15 A (not accessible), breaking capacity 100 A	25 A (not accessible), breaking capacity 300 A
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: 16 A characteristic B or C				
Output					
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage			
Rated voltage Vout DC	24 V	24 V	12 V	24 V	24 V
Total tolerance, static ±	1 %	1 %	2 %	1 %	2 %
Static mains compensation, approx.	0.1 %	0.1 %	0.2 %	0.1 %	0.1 %
Static load balancing, approx.	0.3 %	0.3 %	1.3 %	0.2 %	0.6 %
Residual ripple peak-peak, max.	150 mV				
Residual ripple peak-peak, typ.	15 mV	70 mV	10 mV	30 mV	20 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	250 mV				
Spikes peak-peak, typ. (bandwidth: 20 MHz)	40 mV	220 mV	30 mV	70 mV	40 mV
Adjustment range	24 28 V	24 28 V	12 15.5 V	24 28 V	24 28 V
Product function Output voltage adjustable	Yes	Yes	Yes	Yes	Yes
Output voltage setting	via potentiometer				
Status display On/off behavior	Green LED for 24 V OK No overshoot of V <sub>out</sub> (soft start)	Green LED for 24 V OK No overshoot of V <sub>out</sub> (soft start)	Green LED for 12 V OK No overshoot of V <sub>out</sub> (soft start)	Green LED for 24 V OK No overshoot of V <sub>out</sub> (soft start)	Green LED for 24 V OI No overshoot of V <sub>out</sub> (soft start)
Startup delay, max.	0.5 s				
Voltage rise, typ.	10 ms				
Voltage increase time of the output voltage maximum	20 ms				
Rated current value Iout rated	5 A	5 A	8 A	3.5 A	4 A
Current range	0 6 A	06A	08A	0 3.5 A	0 4 A
Note	6 A up to +40°C; +60 +70 °C: Derating 2%/K	6 A up to +40°C; +60 +70 °C: Derating 2%/K	+60 +70 °C: Derating 2%/K	+60 +70 °C: no Derating	+60 +70 °C: Derating 2%/K
Supplied active power typical	130 W	130 W	107 W	91 W	108 W
Parallel switching for enhanced performance	Yes	Yes	Yes	Yes	Yes
Numbers of parallel switchable units for enhanced performance	2	2	2	2	2

### SITOP PSU3400

Article number	6EP3133-0TA00-0AY0	6EP3233-0TA00-0AY0	6EP3123-0TA00-0AY0	6EP3233-0TA10-0AY0	6EP3133-0TA10-0AY
Product	SITOP PSU3400	SITOP PSU3400	SITOP PSU3400	SITOP PSU3400	SITOP PSU3400
Power supply, type	24 V/5 A	24 V/5 A	12 V/8 A	24 V/3.5 A	24 V/4 A
Efficiency					
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	93 %	92 %	90 %	90 %	89 %
Power loss at <i>V<sub>out rated</sub>, I<sub>out rated</sub>, approx.</i>	10 W	10 W	11 W	7 W	12 W
Power loss [W] during no-load operation maximum	1.5 W	1.5 W	1.5 W	1.5 W	1.5 W
Closed-loop control					
Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	0.3 %	0.3 %	0.3 %	0.3 %	0.3 %
Dynamic load smoothing ( <i>I<sub>out</sub>: 50/100/50 %), U<sub>out</sub> ± typ.</i>	2 %	2 %	4 %	2 %	2 %
Load step setting time 50 to 100%, typ.	1 ms	1 ms	2 ms	1 ms	1 ms
Load step setting time 100 to 50%, typ.	1 ms	1 ms	2 ms	1 ms	1 ms
Protection and monitoring					
Output overvoltage protection	$V_{\rm out}$ < 35 V	$V_{\rm out}$ < 35 V	$V_{out} < 22 V$	$V_{\rm out}$ < 35 V	$V_{\rm out}$ < 35 V
Current limitation, typ.	6.5 A	6.5 A	9 A	3.8 A	4.5 A
Property of the output Short-circuit proof	Yes	Yes	Yes	Yes	Yes
Short-circuit protection	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart	Electronic shutdowr automatic restart
Overload/short-circuit indicator	Yellow LED overload	Yellow LED overload	Yellow LED overload	Yellow LED overload	Yellow LED overload
Safety					
Primary/secondary isolation	Yes	Yes	Yes	Yes	Yes
Galvanic isolation	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Safety extra low output voltage $V_{\rm out}$ according to EN 60950-1	Safety extra low output voltage $V_{\rm out}$ according to EN 60950-1	Safety extra low output voltage $V_{out}$ according to EN 60950-1	Safety extra low outp voltage V <sub>out</sub> accordi to EN 60950-1
Protection class	Class III	Class III	Class III	Class III	Class III
CE mark	Yes	Yes	Yes	Yes	Yes
UL/cUL (CSA) approval		cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259		cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	
Explosion protection	-	-	-	-	-
FM approval	-	-	-	-	-
CB approval	Yes	Yes	Yes	Yes	Yes
Marine approval	DNV GL; ABS in process	DNV GL; ABS in process	DNV GL; ABS in process	DNV GL; ABS in process	DNV GL; ABS in process
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20	IP20
EMC					
Emitted interference	EN 61000-6-3	EN 61000-6-3	EN 61000-6-3	EN 61000-6-3	EN 61000-6-3
Supply harmonics limitation	not applicable	not applicable	not applicable	not applicable	not applicable
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data					
Ambient temperature					
<ul> <li>during operation</li> </ul>	-25 +70 °C	-25 +70 °C	-25 +70 °C	-25 +70 °C	-25 +70 °C
- Note	with natural convection	with natural convection	with natural convection	with natural convection	with natural convect
	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
<ul> <li>during transport</li> </ul>	-40 +65 C	+0 100 0	10 111 100 0	10 111 100 0	
<ul><li>during transport</li><li>during storage</li></ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C

### SITOP PSU3400

# Technical specifications (continued)

Article number	6EP3133-0TA00-0AY0	6EP3233-0TA0	0-0AY0	6EP3123-0TA00-0AY0	6EP32	33-0TA10-0AY0	6EP3133-0TA10-0AY0
Product	SITOP PSU3400	SITOP PSU34	00	SITOP PSU3400	SITOP	PSU3400	SITOP PSU3400
Power supply, type	24 V/5 A	24 V/5 A		12 V/8 A	24 V/3.	5 A	24 V/4 A
Mechanics							
Connection technology	screw-type terminals	screw-type terr	minals	screw-type terminals	screw-	type terminals	screw-type terminals
Connections							
Supply input	L, N, FE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, FE: 1 scre terminal each f 0.5 2.5 mm <sup>2</sup> single-core/fine stranded	or	L, N, FE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	termina 0.5 2	E: 1 screw al each for 2.5 mm <sup>2</sup> core/finely ed	L, N, FE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded
Output				+, -: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup>			
Width of the enclosure	32 mm	32 mm		32 mm	32 mm		32 mm
Height of the enclosure	100 mm	100 mm		100 mm	100 mr	n	100 mm
Depth of the enclosure	100 mm	100 mm		100 mm	100 mr	n	100 mm
Required spacing							
• top	50 mm	50 mm		50 mm	50 mm		50 mm
• bottom	50 mm	50 mm		50 mm	50 mm		50 mm
• left	0 mm	0 mm		0 mm	0 mm		0 mm
• right	0 mm	0 mm		0 mm	0 mm		0 mm
Weight, approx.	0.32 kg	0.32 kg		0.32 kg	0.32 kg	]	0.32 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes		Yes	Yes		Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DI EN 60715 35x7		Snaps onto DIN rail EN 60715 35x7.5/15		onto DIN rail '15 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
Electrical accessories	Buffer module	Buffer module		Buffer module	Buffer I	module	Buffer module
MTBF at 40 °C	1 953 545 h	1 965 061 h		1 934 648 h	1 934 6	648 h	1 868 914 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications input voltage a ambient tempe +25 °C (unless otherwise spec	nd erature	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	input v ambier +25 °C	cations at rated oltage and nt temperature (unless ise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
Article number	6EP3134-0TA00-0AY0		6EP31	24-0TA00-0AY0		6EP3234-0TA0	0-0470
Product	SITOP PSU3400			DP PSU3400		SITOP PSU3400	
Power supply, type	24 V/10 A		12 V/1			24 V/10 A	0
Input	24 V/10 A		12 1/15			24 V/10 A	
Input	DC voltage		DC vol	ana		DC voltage	
Note	Startup as of 18 V, dera for 14 18 V DC	ating necessary	Startup	as of 18 V, derating neo 18 V DC	cessary	•	6 V, derating necessary C
Supply voltage							
• at DC	24 24 V		24 2	4 V		48 48 V	
Input voltage							
• at DC	14 32 V		14 3	2 V		28 54 V	
Wide-range input	No		No			No	
Overvoltage resistance	-		-			-	
Mains buffering at <i>I</i> <sub>out rated</sub> , min. Input current	5 ms; at $V_{\rm in}$ = 24 V		5 ms; a	at $V_{in} = 24 \text{ V}$		5 ms; at $V_{\rm in} = 4$	8 V
<ul> <li>at rated input voltage 24 V</li> </ul>	10.8 A		8.4 A			-	
<ul> <li>at rated input voltage 48 V</li> </ul>	-		-			5.4 A	
Switch-on current limiting (+25 °C), max.	15 A		15 A			15 A	
l²t, max.	0.6 A <sup>2.</sup> s		0.6 A <sup>2</sup> .	6		0.5 A <sup>2.</sup> s	
Built-in incoming fuse	25 A (not accessible), breaking capacity 300	A	25 A (n	not accessible), ng capacity 300 A		15 A (not acces breaking capac	
Protection in the mains power input (IEC 898)	Recommended miniatu breaker: 16 A characte	ire circuit		mended miniature circu r: 16 A characteristic B			I miniature circuit characteristic B or C

### SITOP PSU3400

Article number Product Power supply, type	6EP3134-0TA00-0AY0 SITOP PSU3400 24 V/10 A	6EP3124-0TA00-0AY0 SITOP PSU3400 12 V/15 A	6EP3234-0TA00-0AY0 SITOP PSU3400 24 V/10 A
Output			
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage Vout DC	24 V	12 V	24 V
Total tolerance, static $\pm$	1%	2 %	1%
Static mains compensation, approx.	0.1 %	0.2 %	0.1 %
Static load balancing, approx.	0.3 %	1 %	0.3 %
Residual ripple peak-peak, max.	150 mV	150 mV	150 mV
Residual ripple peak-peak, typ.	30 mV	30 mV	50 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	250 mV	250 mV	250 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	50 mV	50 mV	70 mV
Adjustment range	24 28 V	12 15.5 V	24 28 V
Product function Output voltage adjustable	Yes	Yes	Yes
Output voltage setting	via potentiometer	via potentiometer	via potentiometer
Status display	Green LED for 24 V OK	Green LED for 12 V OK	Green LED for 24 V OK
Signaling	Relay contact (NO contact, contact rating 30 V AC/0.5 A; 60 V DC/0.3 A; 30 V DC/1 A) for 24 V O.K.	Relay contact (NO contact, contact rating 30 V AC/0.5 A; 60 V DC/0.3 A; 30 V DC/1 A) for 12 V O.K.	Relay contact (NO contact, conta rating 30 V AC/0.5 A; 60 V DC/0.3 30 V DC/1 A) for 24 V O.K.
On/off behavior	No overshoot of $V_{out}$ (soft start)	No overshoot of $V_{out}$ (soft start)	No overshoot of $V_{out}$ (soft start)
Startup delay, max.	0.5 s	0.5 s	0.5 s
Voltage rise, typ.	10 ms	5 ms	10 ms
Voltage increase time of the output voltage maximum	20 ms	10 ms	20 ms
Rated current value Iout rated	10 A	15 A	10 A
Current range	0 12.5 A	0 15 A	0 12.5 A
Note	12 A up to +40°C; +60 +70 °C: Derating 2%/K	+60 +70 °C: Derating 2%/K	12 A up to +40°C; +60 +70 °C: Derating 2%/K
Supplied active power typical	260 W	200 W	256 W
Parallel switching for enhanced performance	Yes	Yes	Yes
Numbers of parallel switchable units for enhanced performance	2	2	2
Efficiency	00.0%		00 F 01
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	93 %	91 %	93.5 %
Power loss at <i>V<sub>out rated</sub>, I<sub>out rated</sub>, approx. Power loss [W] during no-load</i>	20 W 1.5 W	21 W 0.5 W	17 W 1.5 W
operation maximum		0.0 1	
Closed-loop control			
Dynamic mains compensation ( <i>V<sub>in rated</sub> ±</i> 15 %), max.	0.3 %	0.3 %	0.3 %
Dynamic load smoothing ( <i>l<sub>out</sub>: 50/100/50 %), U<sub>out</sub> ± typ.</i>	2 %	4 %	2 %
Load step setting time 50 to 100%, typ.	1 ms	2 ms	1 ms
Load step setting time 100 to 50%, typ.	1 ms	2 ms	1 ms
Protection and monitoring			
Output overvoltage protection	U <sub>a</sub> < 35 V	U <sub>a</sub> < 22 V	U <sub>a</sub> < 35 V
Current limitation, typ.	13 A	16 A	13 A
Property of the output Short-circuit proof	Yes	Yes	Yes
Short-circuit protection	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart Yellow LED overload	Electronic shutdown, automatic re Yellow LED overload

### SITOP PSU3400

### Technical specifications (continued)

Article number	6EP3134-0TA00-0AY0	6EP3124-0TA00-0AY0	6EP3234-0TA00-0AY0
Product	SITOP PSU3400	SITOP PSU3400	SITOP PSU3400
Power supply, type	24 V/10 A	12 V/15 A	24 V/10 A
Safety			
Primary/secondary isolation	Yes	Yes	Yes
Galvanic isolation	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Safety extra low output voltage $V_{out}$ according to EN 60950-1	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1
Protection class	Class III	Class III	Class III
CE mark	Yes	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
Explosion protection	-	-	
FM approval	-	-	
CB approval	Yes	Yes	Yes
Marine approval	DNV GL; ABS in process	DNV GL; ABS in process	DNV GL; ABS in process
Degree of protection (EN 60529)	IP20	IP20	IP20
EMC			
Emitted interference	EN 61000-6-3	EN 61000-6-3	EN 61000-6-3
Supply harmonics limitation	not applicable	not applicable	not applicable
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data			
Ambient temperature			
<ul> <li>during operation</li> </ul>	-25 +70 °C	-25 +70 °C	-25 +70 °C
- Note	with natural convection	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics			
Connection technology	screw-type terminals	screw-type terminals	screw-type terminals
Connections			
Supply input	L, N, FE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, FE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, FE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded
Output	+, -: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup>	+, -: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup>	+, -: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup>
Auxiliary	Alarm signals: 2 screw terminals for 0.5 2.5 mm <sup>2</sup>	Alarm signals: 2 screw terminals for 0.5 2.5 mm <sup>2</sup>	Alarm signals: 2 screw terminals for 0.5 2.5 mm <sup>2</sup>
Connections signaling contact	2 screw terminals for 0.5 $\dots$ 2.5 $\mbox{mm}^2$	2 screw terminals for 0.5 2.5 mm <sup>2</sup>	2 screw terminals for 0.5 2.5 mm <sup>2</sup>
Width of the enclosure	42 mm	42 mm	42 mm
Height of the enclosure	125 mm	125 mm	125 mm
Depth of the enclosure	120 mm	120 mm	120 mm
Required spacing			
• top	50 mm	50 mm	50 mm
• bottom	50 mm	50 mm	50 mm
• left	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm
Weight, approx.	0.6 kg	0.6 kg	0.6 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
MTBF at 40 °C	1 579 080 h	1 411 273 h	1 552 337 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

CIT	PSI	124	00
511	<b>F</b> SU	J34	υU

Ordering data	Article No.	More information
SITOP PSU3400	6EP3134-0TA00-0AY0	Select the appropriate power supply quickly and easily with t
DC/DC stabilized power supply Input: 24 V DC (18 32 V) Output: 24 V DC/10 A		TIA Selection Tool: http://www.siemens.com/tst
SITOP PSU3400	6EP3124-0TA00-0AY0	
DC/DC stabilized power supply Input: 24 V DC (18 32 V) Output: 12 V DC/15 A		
SITOP PSU3400	6EP3234-0TA00-0AY0	
DC/DC stabilized power supply Input: 48 V DC (32 54 V) Output: 24 V DC/10 A		
SITOP PSU3400	6EP3133-0TA00-0AY0	
DC/DC stabilized power supply Input: 24 V DC (18 32 V) Output: 24 V DC/5 A		
SITOP PSU3400	6EP3233-0TA00-0AY0	
DC/DC stabilized power supply Input: 48 V DC (36 60 V) Output: 24 V DC/5 A		
SITOP PSU3400	6EP3123-0TA00-0AY0	
DC/DC stabilized power supply Input: 24 V DC (18 32 V) Output: 12 V DC/8 A		
SITOP PSU3400	6EP3233-0TA10-0AY0	
DC/DC stabilized power supply Input: 48 V DC (36 60 V) Output: 24 V DC/3.5 A NEC Class 2		
SITOP PSU3400	6EP3133-0TA10-0AY0	
DC/DC stabilized power supply Input: 12 V (9 18 V) Output: 24 V DC/4 A		

#### SITOP PSU400M

#### Overview



The SITOP PSU400M power supply with a 600 V DC input is suitable as an efficient DC/DC converter for drive and battery systems; wide input and temperature range, high efficiency; slim design; with 50% extra power for 5 s/min. A voltage surge limiter is available as an accessory as ballast for the PSU400M. This gives the option of connecting the DC/DC converter directly to a DC voltage of up to 900 V DC.

Article number Product	6EP1536-3AA00 SITOP PSU400M	Article number Product	6EP1536-3AA00 SITOP PSU400M
Power supply, type	24 V/20 A	Power supply, type	24 V/20 A
Input		Output (continued)	
Input • Note	DC voltage startup from 340 V DC;	Status display	Green LED for 24 V OK, green flashing LED for start delay
	derating necessary at 300 400 V DC and 824 900 V DC	Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A; 30 V DC/1 A) for 24 V OK
Supply voltage		On/off behavior	No overshoot of Vout (soft start)
• at DC	600 600 V	Startup delay, max.	0.1 s; 10 s adjustable using switch
Input voltage • at DC	300 900 V	Voltage increase time of the output voltage maximum	150 ms
Overvoltage resistance	Shutdown at $V_{in} > 900 \text{ V DC}$	Rated current value Iout rated	20 A
Input current		Current range	0 20 A
at DC at rated input voltage 600 V	0.85 A	Note	+60 +70 °C: Derating 5.5%/K
Switch-on current limiting (+25 °C),	8 A	Supplied active power typical	480 W
max.		Short-term overload current	
l²t, max.	0.02 A <sup>2.</sup> s	<ul> <li>on short-circuiting during the</li> </ul>	40 A
Built-in incoming fuse	yes, cut-off capacity 20 kA;	start-up typical	CO A
Output	L/R < 2 ms ("+" and "-" input)	<ul> <li>at short-circuit during operation typical</li> </ul>	60 A
Output	Controlled, isolated DC voltage	Duration of overloading capability for excess current	
Rated voltage Vout DC	24 V	<ul> <li>on short-circuiting during the</li> </ul>	150 ms
Total tolerance, static ±	3 %	start-up	
Static mains compensation, approx.	0.3 %	<ul> <li>at short-circuit during operation</li> </ul>	25 ms
Static load balancing, approx.	0.3 %	Constant overload current	
Residual ripple peak-peak, max.	150 mV	<ul> <li>on short-circuiting during the start up turing.</li> </ul>	23 A
Residual ripple peak-peak, typ.	30 mV	start-up typical	
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV	Parallel switching for enhanced performance	Yes; switchable characteristic
Spikes peak-peak, typ. (bandwidth: 20 MHz)	100 mV	Numbers of parallel switchable units for enhanced performance	2
Adjustment range	24 28.8 V		
Product function Output voltage adjustable	Yes		
Output voltage setting	via potentiometer; max. 480 W		

6EP1536-3AA00 SITOP PSU400M 24 V/20 A

EN 61000-6-2

-25 ... +70 °C with natural convection -40 ... +85 °C -40 ... +85 °C

screw-type terminals

finely stranded

90 mm

125 mm 125 mm

50 mm 50 mm 0 mm 0 mm 1.2 kg

Yes

622 277 h

Snaps onto DIN rail EN 60715 35x7.5/15 Device identification label

20 mm × 7 mm, pale turquoise 3RT1900-1SB20

Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

EN 55022 Class A (emission)

Climate class 3K3, no condensation

DC input, +, -, PE: 1 screw terminal each for 0.2 ... 6/4 mm<sup>2</sup> single-core/

Alarm signals: 2 screw terminals for 0.14 ... 1.5  $\text{mm}^2$  single-core/finely stranded

+, -: 2 screw terminals each for 0.2 ... 6/4 mm<sup>2</sup> single-core/finely stranded

#### SITOP PSU400M

Article number	6EP1536-3AA00	Article number
Product	SITOP PSU400M	Product
Power supply, type	24 V/20 A	Power supply, type
Efficiency		EMC
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	95 %	Emitted interference Supply harmonics limitation
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	25 W	Noise immunity
Closed-loop control		Operating data
Dynamic mains compensation $(V_{in} \text{ rated } \pm 15 \%)$ , max.	1.5 %	<ul><li>Ambient temperature</li><li>during operation</li></ul>
Dynamic load smoothing $(I_{out}: 50/100/50 \%), U_{out} \pm typ.$	1.5 %	<ul><li>Note</li><li>during transport</li></ul>
Load step setting time 50 to 100%, typ.	1 ms	during storage
Load step setting time 100 to 50%, typ.	1 ms	Humidity class according to EN 60721
Setting time maximum	5 ms	Mechanics
Protection and monitoring	0113	Connection technology
Output overvoltage protection	< 33 V	Connections
Current limitation, typ.	22 A	<ul> <li>Supply input</li> </ul>
Property of the output Short-circuit proof	Yes	Output
Short-circuit protection	Alternatively, constant current characteristic approx. 22 A or latching shutdown	Auxiliary
Enduring short circuit current RMS value		
typical	22 A	Width of the enclosure
Overcurrent overload capability in normal operation	overload capability 150 % <i>l</i> <sub>out rated</sub>	Height of the enclosure Depth of the enclosure
Overload/short-circuit indicator	LED yellow for "overload", LED red for "latching shutdown", red LED flashing for "Overtemperature"	Required spacing <ul> <li>top</li> </ul>
Safety		<ul> <li>bottom</li> </ul>
Primary/secondary isolation	Yes	• left
Galvanic isolation	Protective extra low output voltage Vout according to EN 60950-1 and	<ul> <li>right</li> <li>Weight, approx.</li> </ul>
Protection class	EN 50178 Class I	Product feature of the enclosu housing for side-by-side mour
CE mark	Yes	Installation
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	Mechanical accessories
Explosion protection	-	
FM approval	-	MTBF at 40 °C
CB approval	Yes	Other information
Marine approval	DNV GL	Other Information
Degree of protection (EN 60529)	IP20	

Ordering data	Article No.	Accessories	Article No.
SITOP PSU400M, 1-phase, 24 V DC/20 A	6EP1536-3AA00	Device identification label SITOP PSU400M voltage surge	3RT2900-1SB20 6EP1566-3AA00
Stabilized power supply Input: 600 V AC Output: 24 V DC/20 A		limiter	

#### Siemens KT 10.1 · 2019/2020 6/11

Other DC/DC converters

48-220 V DC/24 V DC/0.375 A

### Overview



The optimum power supply for automation solutions in the lower performance range; with wide range input for 48-220 V DC. Thanks to their compact and slim design, they are particularly suitable for use where space is limited and in conjunction with low-voltage switchgear.

Article number	6EP1731-2BA00	
Product	SITOP power	
Power supply, type	24 V/0.375 A	
Input		
Input	DC voltage	
Voltage range AC	30 187 V	
Supply voltage		
• at DC	48 220 V	
Input voltage		
• at DC	30 264 V	
Wide-range input	Yes	
Overvoltage resistance	-	
Mains buffering at Iout rated, min.	10 ms; at V <sub>in</sub> = 220 V	
Input current		
<ul> <li>at rated input voltage 48 V</li> </ul>	0.3 A	
<ul> <li>at rated input voltage 220 V</li> </ul>	0.06 A	
Switch-on current limiting (+25 °C), max.	35 A	
Duration of inrush current limiting at 25 °C		
<ul> <li>typical</li> </ul>	3 ms	
l²t, max.	1.2 A <sup>2</sup> ·s	
Built-in incoming fuse	F 4 A/250 V (not accessible)	
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 6 A characteristic C, suitable for DC	

Article number	6EP1731-2BA00	
Product	SITOP power	
Power supply, type	24 V/0.375 A	
Output		
Output	Controlled, isolated DC voltage	
Rated voltage Vout DC	24 V	
Total tolerance, static ±	3 %	
Static mains compensation, approx.	0.1 %	
Static load balancing, approx.	0.1 %	
Residual ripple peak-peak, max.	150 mV	
Residual ripple peak-peak, typ.	50 mV	
Spikes peak-peak, max. (bandwidth: 20 MHz)	240 mV	
Spikes peak-peak, typ. (bandwidth: 20 MHz)	50 mV	
Product function Output voltage adjustable	No	
Output voltage setting	-	
Status display	Green LED for 24 V OK	
On/off behavior	No overshoot of Vout (soft start)	
Startup delay, max.	2.5 s	
Voltage rise, typ.	90 ms	
Rated current value <i>l</i> out rated	0.375 A	
Current range	0 0.375 A	
Note	+60 +70 °C: Derating 3%/K	
Supplied active power typical	9 W	
Short-term overload current		
<ul> <li>at short-circuit during operation typical</li> </ul>	2.7 A	
Duration of overloading capability for excess current		
<ul> <li>at short-circuit during operation</li> </ul>	200 ms	
Parallel switching for enhanced performance	No	

## 48-220 V DC/24 V DC/0.375 A

Article number	6EP1731-2BA00	Article nu
Product	SITOP power	Product
Power supply, type	24 V/0.375 A	Power sup
Efficiency		EMC
Efficiency at Vout rated, Iout rated,	66 %	Emitted int
approx.		Supply har
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	4.6 W	Noise imm
Closed-loop control		Operating
Dynamic mains compensation	0.3 %	Ambient te
(V <sub>in rated</sub> ±15 %), max.		<ul> <li>during op</li> </ul>
Dynamic load smoothing	0.4 %	- Note
$(I_{out}: 50/100/50 \%), U_{out} \pm typ.$	2 ma	<ul> <li>during transition</li> </ul>
Load step setting time 50 to 100%, typ.	2 ms	<ul> <li>during st</li> </ul>
Load step setting time 100 to 50%,	2 ms	Humidity c EN 60721
typ.		Mechanics
Protection and monitoring		Connection
Output overvoltage protection	Yes, according to EN 60950-1	Connectior
Current limitation	0.41 0.49 A	<ul> <li>Supply ir</li> </ul>
Property of the output Short-circuit proof	Yes	,
Short-circuit protection	Electronic shutdown, automatic restart	<ul> <li>Output</li> </ul>
Enduring short circuit current RMS value		
• maximum	0.9 A	<ul> <li>Auxiliary</li> </ul>
Overload/short-circuit indicator	-	Width of th
Safety		Height of t
Primary/secondary isolation	Yes	Depth of th
Galvanic isolation	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178	Required s <ul> <li>top</li> </ul>
Protection class	Class I	<ul> <li>bottom</li> </ul>
Leakage current		<ul> <li>left</li> </ul>
• maximum	3.5 mA	<ul> <li>right</li> </ul>
CE mark	Yes	Weight, ap
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 142), File E143289, cURus-Recognized (UL 60950, CSA C22.2 No. 60950), File E151273	Product fea housing for Installation
Explosion protection	-	
FM approval	-	MTBF at 40
CB approval	No	Other infor
Marine approval	-	

Article number	6EP1731-2BA00
Product	SITOP power
Power supply, type	24 V/0.375 A
EMC	
Emitted interference	EN 55022 Class B
Supply harmonics limitation	not applicable
Noise immunity	EN 61000-6-2
Operating data	
Ambient temperature	
<ul> <li>during operation</li> </ul>	-25 +70 °C
- Note	with natural convection
<ul> <li>during transport</li> </ul>	-40 +70 °C
<ul> <li>during storage</li> </ul>	-40 +70 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation
Mechanics	
Connection technology	screw-type terminals
Connections	
Supply input	L+1, M1, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded
Output	+: 1 screw terminal for 0.5 2.5 mm <sup>2</sup> ; -: 2 screw terminals for 0.5 2.5 mm <sup>2</sup>
Auxiliary	_
Width of the enclosure	22.5 mm
Height of the enclosure	80 mm
Depth of the enclosure	91 mm
Required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
Weight, approx.	0.14 kg
Product feature of the enclosure housing for side-by-side mounting	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15
MTBF at 40 °C	1 466 123 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Article No.

6EP1731-2BA00

## Ordering data

#### SITOP power 0.375 A

DC/DC stabilized power supply Input: DC 48 ... 220 V Output: 24 V DC/0.375 A

## **DC/DC** converter

Other DC/DC converters

48-110 V DC/24 V DC/2 A

### Overview



## Technical specifications

Article number	6EP1732-0AA00
Product	SITOP power
Power supply, type	24 V/2 A
Input	
Input	DC voltage
Supply voltage	
• at DC	48 110 V
Input voltage	
• at DC	38 121 V
Wide-range input	Yes
Overvoltage resistance	-
Mains buffering at Iout rated, min.	5 ms; at $V_{in}$ = 48 V
Input current	
<ul> <li>at rated input voltage 48 V</li> </ul>	1.2 A
<ul> <li>at rated input voltage 110 V</li> </ul>	0.5 A
Switch-on current limiting (+25 °C), max.	33 A
Built-in incoming fuse	T 2.5 A (not accessible)
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: 10 to 25 A characteristic B or 6 to 25 A characteristic C, suitable for DC

The DC/DC converter for supply from battery and DC systems; with a wide input voltage range from 38 V to 121 V DC.

Article number	6EP1732-0AA00
Product	SITOP power
Power supply, type	24 V/2 A
Output	
Output	Controlled, isolated DC voltage
Rated voltage Vout DC	24 V
Total tolerance, static ±	1 %
Static mains compensation, approx.	0.1 %
Static load balancing, approx.	0.4 %
Residual ripple peak-peak, max.	100 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	300 mV
Adjustment range	23.5 26.5 V
Product function Output voltage adjustable	Yes
Output voltage setting	via potentiometer
Status display	Green LED for 24 V OK
On/off behavior	Overshoot of V <sub>out</sub> on startup max. 25 V
Startup delay, max.	3 s
Voltage rise, typ.	30 ms
Rated current value Iout rated	2 A
Current range	0 2 A
Supplied active power typical	48 W
Parallel switching for enhanced performance	Yes
Numbers of parallel switchable units for enhanced performance	2

## 48-110 V DC/24 V DC/2 A

Article number	6EP1732-0AA00	Article number
Product	SITOP power	Product
Power supply, type	24 V/2 A	Power supply
Efficiency		EMC
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	84 %	Emitted interfe Supply harmo
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	9 W	Noise immunit
Closed-loop control		Operating dat
Dynamic mains compensation $(V_{\text{in rated}} \pm 15 \%)$ , max.	0.3 %	Ambient temp <ul> <li>during operative</li> </ul>
Dynamic load smoothing (I <sub>out</sub> : 50/100/50 %), U <sub>out</sub> ± typ.	0.8 %	<ul><li>Note</li><li>during trans</li></ul>
Load step setting time 50 to 100%, typ.	2.5 ms	<ul> <li>during stora</li> </ul>
Load step setting time 100 to 50%, typ.	2.5 ms	Humidity class EN 60721
Protection and monitoring		Mechanics
Output overvoltage protection	Yes, suppressor diode at output	Connection te
Current limitation	2.1 3 A	Connections
Property of the output Short-circuit proof	Yes	<ul> <li>Supply inpu</li> </ul>
Short-circuit protection	Electronic shutdown, automatic restart	Output
Enduring short circuit current RMS value		<ul> <li>Auxiliary</li> <li>Width of the e</li> </ul>
• maximum	2 A	Height of the
Overload/short-circuit indicator	-	Depth of the e
Safety		•
Primary/secondary isolation	Yes	Required spa
Galvanic isolation	Safety extra low output voltage $V_{\rm out}$ according to EN 60950-1	<ul><li>top</li><li>bottom</li></ul>
Protection class	Class I	<ul> <li>left</li> </ul>
Leakage current		<ul> <li>right</li> </ul>
• maximum	3.5 mA	Weight, appro
typical	0.7 mA	Product featur housing for si
CE mark	Yes	0
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 142), File E179336	Installation MTBF at 40 °C
Explosion protection	-	Other informa
FM approval	-	
CB approval	No	
Marine approval	-	
Degree of protection (EN 60529)	IP20	Ordering da

Article number Product	6EP1732-0AA00 SITOP power
Power supply, type	24 V/2 A
EMC	
Emitted interference	EN 55022 Class B
Supply harmonics limitation	not applicable
Noise immunity	EN 61000-6-2
Operating data	
Ambient temperature	
<ul> <li>during operation</li> </ul>	0 70 °C
- Note	with natural convection
<ul> <li>during transport</li> </ul>	-40 +70 °C
<ul> <li>during storage</li> </ul>	-40 +70 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation
Mechanics	
Connection technology	screw-type terminals
Connections	
Supply input	L+, M1, PE: 1 screw terminal each for 2 x 0.5 2.5/1.5 mm <sup>2</sup> single-core/ finely stranded
Output	L+, M: 1 screw terminal each for 2 x 0.5 2.5 mm <sup>2</sup>
Auxiliary	-
Width of the enclosure	80 mm
Height of the enclosure	135 mm
Depth of the enclosure	120 mm
Required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
Weight, approx.	0.5 kg
Product feature of the enclosure housing for side-by-side mounting	Yes
Installation	Snaps onto DIN rail EN 60715 35x15
MTBF at 40 °C	1 580 078 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
Ordering data	Article No.
SITOP power 2 A	6EP1732-0AA00

DC/DC stabilized power supply Input: DC 48/60/110 V Output: 24 V DC/2 A

## **DC/DC** converter

Other DC/DC converters

24 V DC/12 V DC/2.5 A

## Overview



DC/DC converter for connection to 24 V DC networks over permanent wiring. Output voltage 12 V DC; floating, short circuit-proof, open circuit-proof.

Article number	6EP1621-2BA00
Product	SITOP DC/DC
Power supply, type	12 V/2.5 A
Input	
Input	DC voltage PELV/SELV
Supply voltage	
• at DC	24 24 V
Input voltage	
• at DC	18.5 30.2 V
Wide-range input	No
Input current	
<ul> <li>at rated input voltage 24 V</li> </ul>	2.5 A
Switch-on current limiting (+25 °C), max.	20 A
Duration of inrush current limiting at 25 °C	
<ul> <li>typical</li> </ul>	5 ms
Built-in incoming fuse	not accessible
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: 10 A characteristic B

Article number	6EP1621-2BA00
Product	SITOP DC/DC
Power supply, type	12 V/2.5 A
Output	
Output	Controlled, isolated DC voltage
Rated voltage Vout DC	12 V
Total tolerance, static ±	3 %
Static mains compensation, approx.	0.1 %
Static load balancing, approx.	0.4 %
Residual ripple peak-peak, max.	100 mV
Residual ripple peak-peak, typ.	50 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	50 mV
Adjustment range	12 14 V
Product function Output voltage adjustable	Yes
Output voltage setting	via potentiometer; max. 120 W
Status display	Green LED for 12 V OK
Startup delay, max.	0.5 s
Voltage rise, typ.	300 ms
Rated current value Iout rated	2.5 A
Current range	0 2.5 A
Short-term overload current	
<ul> <li>on short-circuiting during the start-up typical</li> </ul>	3.3 A
<ul> <li>at short-circuit during operation typical</li> </ul>	3.3 A
Constant overload current	
<ul> <li>on short-circuiting during the start-up typical</li> </ul>	3.3 A
<ul> <li>at short-circuit during operation typical</li> </ul>	3.3 A
Parallel switching for enhanced performance	Yes
Numbers of parallel switchable units for enhanced performance	2

# 24 V DC/12 V DC/2.5 A

Article number	6EP1621-2BA00
Product	SITOP DC/DC
Power supply, type	12 V/2.5 A
fficiency	
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	83 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	6.1 W
losed-loop control	
Dynamic mains compensation V <sub>in rated</sub> ±15 %), max.	0.5 %
Dynamic load smoothing I <sub>out</sub> : 50/100/50 %), <i>U</i> <sub>out</sub> ± typ.	3 %
oad step setting time 0 to 100%, typ.	5 ms
oad step setting time 00 to 50%, typ.	2 ms
Setting time maximum	5 ms
rotection and monitoring	
Dutput overvoltage protection	< 24 V
Current limitation	3 3.6 A
Current limitation, typ.	3.3 A
Property of the output Short-circuit proof	Yes
Short-circuit protection	Constant current characteristic approx. 3.2 A
Enduring short circuit current RMS value	
typical	3.2 A
Overload/short-circuit indicator	LED red for "overload"
afety	
Primary/secondary isolation	Yes
Galvanic isolation	Safety extra low output voltage Vout according to EN 60950-1
Protection class	Class II
CE mark	Yes
JL/cUL (CSA) approval	cCSAus (UL 508, CSA22.2-107, UL60950-1, CSA22.2-60950-1)
Explosion protection	-
M approval	-
CB approval	No
larine approval	-
Degree of protection (EN 60529)	IP20

Article number	6EP1621-2BA00
Product	SITOP DC/DC
Power supply, type	12 V/2.5 A
EMC	12 1/2.5 A
Emitted interference	EN 55022 Class B
Supply harmonics limitation	-
Noise immunity	EN 61000-6-2
Operating data	
Ambient temperature	
during operation	0 60 °C
- Note	with natural convection
during transport	-40 +85 °C
during storage	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation
Mechanics	
Connection technology	screw-type terminals
Connections	
Supply input	+, -: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>
Output	+, -: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup>
Auxiliary	-
Width of the enclosure	32.5 mm
Height of the enclosure	125 mm
Depth of the enclosure	125 mm
Required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
Weight, approx.	0.32 kg
Product feature of the enclosure housing for side-by-side mounting	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15
MTBF at 40 °C	563 793 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
Ordering data	Article No.
SITOP 2.5 A, DC/DC converter	6EP1621-2BA00
Stabilized power supply	
Input: 24 V AC Output: 12 V DC/2.5 A	

## **DC/DC** converter

Other DC/DC converters

#### Overview



DC/DC converter for connection to 48 V direct voltage networks. Output voltage 24 V DC; floating, short-circuit and no-load proof.

#### Technical specifications

Article number	6EP1733-2BA00-0AA0
Product	SITOP PSU400S
Power supply, type	24 V/5 A
Input	
Input	DC voltage
Input voltage	
• at DC	30 75.5 V
Mains buffering at I <sub>out rated</sub> , min.	5 ms; at <i>V</i> <sub>in</sub> = 48 V
Input current	2.9 A
<ul> <li>at rated input voltage 48 V</li> <li>Protection in the mains power input</li> </ul>	6 A characteristic C
(IEC 898)	6 A characteristic C
Output	
Output	Controlled, isolated DC voltage
Rated voltage Vout DC	24 V
Total tolerance, static ±	3 %
Residual ripple peak-peak, max.	50 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV
Adjustment range	22.8 28 V
Product function Output voltage adjustable	Yes
Output voltage setting	via potentiometer; max. 120 W
Status display	Green LED for 24 V OK
Signaling	No
Startup delay, max.	2.5 s
Voltage increase time of the output voltage maximum	1 500 ms
Rated current value Iout rated	5 A
Current range	0 5 A
Note	+60 +70 °C: Derating 2.5%/K
Supplied active power typical	120 W
Parallel switching for enhanced performance	Yes
Numbers of parallel switchable units for enhanced performance	2
Efficiency	
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	89 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	5 W

#### Technical specifications (continued) 6EP1733-2BA00-0AA0 Article number Product SITOP PSU400S Power supply, type 24 V/5 A Closed-loop control Setting time maximum 1 ms Protection and monitoring Output overvoltage protection < 33 V Property of the output Yes Short-circuit proof Overcurrent overload capability overload capability 150 % Iout rated in normal operation up to 5 s/min Safety Primary/secondary isolation Yes Safety extra low output voltage $V_{\rm out}$ according to EN 60950-1 Galvanic isolation CE mark Yes UL 508, CSA C22.2 No. 107.1 UL/cUL (CSA) approval Explosion protection FM approval Marine approval EMC EN 61000-6-3 Class A Emitted interference Noise immunity EN 61000-6-2 Operating data Ambient temperature -25 ... +70 °C · during operation - Note with natural convection -40 ... +85 °C • during transport -40 ... +85 °C · during storage Humidity class according to EN 60721 Climate class 3K3, no condensation Mechanics Connection technology screw-type terminals Connections +, -: 1 screw terminal each for 0.2 ... 2.5 $\mbox{ mm}^2$ · Supply input +, -: 2 screw terminals each for 0.2 ... 2.5 mm<sup>2</sup> • Output Width of the enclosure 50 mm Height of the enclosure 125 mm Depth of the enclosure 125 mm Required spacing • top 50 mm 50 mm bottom 0 mm left right 0 mm 0.5 kg Weight, approx. Product feature of the enclosure Yes housing for side-by-side mounting Installation Snaps onto DIN rail EN 60715 35x7.5/15 Electrical accessories Redundancy module, buffer module, diagnostics module SITOP select, DC UPS MTBF at 40 °C 500 000 h Other information Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified) Ordering data Article No. 6EP1733-2BA00-0AA0 SITOP PSU400S 24 V/5 A, DC/DC converter

Stabilized power supply Input: 48 V DC (30.2 ... 75 V) Output: 24 V DC/5 A © Siemens 2019

## Special designs, special uses



#### 7/2 Introduction

- Wall mounting 1-phase, 12 V DC (PSU100D)
- 1-phase, 24 V DC (PSU100D)
- 7/10 High degree of protection
- 7/10 1-phase, 24 V DC (SITOP PSU100P, IP67)
  - 3-phase, 24 V DC (ET200pro PS, IP67)
- 7/16 Battery charging
- 7/16 3-phase, 12 V DC
- 7/18 3-phase, 24 V DC
- Medical applications
- 1-phase, 24 V DC
- 3-phase, 24 V DC
- Alternative output voltages
- 1-phase, 2 x 15 V DC
- (SITOP PSU3600 dual)
- 1-phase, 3-52 V DC (SITOP PSU3600 flexi)
- Special uses
- 1-phase, 24 V DC
- 1-phase, 48 V DC (SITOP PSU100E)
- 3-phase, 24 V DC (SITOP PSU300E)
- SIPLUS power supplies
- Introduction
- Ordering data
- 7/40 AS-Interface power supply units 7/40
  - 1-phase / 1-2-phase / DC, AS-i 30 V
- (with data decoupling) 7/41 1-phase, 30 V DC (without data decoupling)

#### Introduction

#### Overview



#### Well prepared for special tasks and conditions

Whether restricted installation conditions, harsh ambient conditions, or special input or output voltages are concerned: These standard power supply units ensure a reliable and efficient supply of power, even when subject to extraordinary demands. Thanks to their compact design they can be integrated perfectly into existing installations.

## More information

Select the appropriate power supply quickly and easily with the TIA Selection Tool: http://www.siemens.com/tst

Introduction

## Overview



#### Low-cost power supply for wall mounting

The PSU100D switch mode power supplies extend the Siemens power supply portfolio to include single-phase devices for direct wall mounting using screws. The flat and rugged aluminum enclosure with IP20 degree of protection can be installed in various orientations and is therefore ideal for installation locations with limited space or for mounting in control cabinets and enclosures without a DIN rail. The low-cost devices meet all the basic requirements for a power supply, typical applications being apparatus, automated equipment and automation solutions.

#### Main product highlights

- For 12-V standard applications from 3 A to 8.3 A
- For 24 V standard applications from 2.1 A to 12.5 A
- Compact metal enclosure
- Wide-range input
- Green LED for "24 V OK"
- Certification in accordance with CE and UL
- Adjustable output voltage from 22 to 28 V or from 11 to 14 V for compensating voltage drops
- Temperature range from -10 °C to +70 °C

Wall mounting

### 1-phase, 12 V DC (PSU100D)

#### Overview



The single-phase PSU100D are switch mode power supplies for direct wall mounting using screws. The flat and rugged aluminum enclosure with IP20 degree of protection can be installed in various orientations and is therefore ideal for installation locations with limited space or for mounting in control cabinets and enclosures without a DIN rail. The low-cost devices meet all the basic requirements for a power supply, typical applications being apparatus, automated equipment and automation solutions.

#### Main product highlights

- 12 V DC, 3 A and 8.3 A
- Compact metal enclosure
- Wide-range input
- Green LED for "24 V OK"
- Certification in accordance with CE and UL
- Adjustable output voltage from 22 to 28 V or from 11 to 14 V for compensating voltage drops
- Temperature range from -10 °C to +70 °C

Article number	6EP1321-1LD00	6EP1322-1LD00
Product	PSU100D	PSU100D
Power supply, type	12 V/3 A	12 V/8.3 A
Input		
Input	1-phase AC	1-phase AC
Rated voltage value Vin rated	100 240 V	100 240 V
Voltage range AC	85 264 V	85 264 V
Wide-range input	Yes	Yes
Mains buffering at Iout rated, min.	15 ms; at V <sub>in</sub> = 115/230 V	15 ms; at V <sub>in</sub> = 115/230 V
Rated line frequency 1	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz
Input current		
<ul> <li>at rated input voltage 100 V</li> </ul>	0.75 A	2 A
<ul> <li>at rated input voltage 240 V</li> </ul>	0.5 A	1.1 A
Switch-on current limiting (+25 °C), max.	60 A	75 A
l²t, max.	1.2 A <sup>2.</sup> s	5.5 A <sup>2</sup> ·s
Built-in incoming fuse	internal	internal
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 10 A characteristic C or from 16 A characteristic B	Recommended miniature circuit breaker: from 10 A characteristic C or from 16 A characteristic B

# Special designs, special uses Wall mounting

1-phase, 12 V DC (PSU100D)

Article number	6EP1321-1LD00	6EP1322-1LD00
Product	PSU100D	PSU100D
Power supply, type	12 V/3 A	12 V/8.3 A
Output		
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage V <sub>out</sub> DC	12 V	12 V
Total tolerance, static $\pm$	2 %	2 %
Static mains compensation, approx.	0.5 %	0.5 %
Static load balancing, approx.	1 %	1 %
Residual ripple peak-peak, max.	100 mV	100 mV
Spikes peak-peak, max.	100 mV	100 mV
(bandwidth: 20 MHz)		
Adjustment range	11 14 V	11 14 V
Product function Output voltage adjustable	Yes	Yes
Output voltage setting	via potentiometer	via potentiometer
Status display	Green LED for 12 V OK	Green LED for 12 V OK
On/off behavior	Overshoot of $V_{out} < 2 \%$	Overshoot of $V_{out}$ < 2 %
Startup delay, max.	2.5 s	1 s
Voltage increase time of the output	30 ms	30 ms
voltage maximum		
Rated current value I <sub>out rated</sub>	3 A	8.3 A
Current range	0 3 A	0 8.3 A
Note	+50 +70 °C: Derating 2.5%/K	+50 +70 °C: Derating 2.5%/K
Supplied active power typical	36 W	100 W
Parallel switching for enhanced performance	Yes	Yes
Numbers of parallel switchable units for enhanced performance	2	2
Efficiency		
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	84 %	84 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	6.5 W	19 W
Closed-loop control		
Dynamic mains compensation	0.5 %	0.5 %
(V <sub>in rated</sub> ±15 %), max.		
Dynamic load smoothing (I <sub>out</sub> : 50/100/50 %), U <sub>out</sub> ± typ.	5 %	5 %
Protection and monitoring		
Output overvoltage protection	< 17.6 V	< 17.6 V
Current limitation, typ.	3.6 A	9.9 A
Property of the output Short-circuit proof	Yes	Yes
Short-circuit protection	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart
Enduring short circuit current RMS value		
• typical	6 A	10 A
Overload/short-circuit indicator	-	-
Safety		
Primary/secondary isolation	Yes	Yes
Galvanic isolation	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1
Protection class	Class I	EN 60950-1 Class I
		012551
Leakage current		0.5 m/
• maximum	3.5 mA	3.5 mA
• typical	1 mA	1 mA
CE mark	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus (UL 60950-1, CSA C22.2 No. 60950-1), File E151273	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus (UL 60950-1, CSA C22.2 No. 60950-1), File E151273
Explosion protection		
FM approval	- Voo	- Yoo
CB approval Marine approval	Yes	Yes
	-	-

Wall mounting

# 1-phase, 12 V DC (PSU100D)

Technical specifications (	continued)		
Article number	6EP1321-1LD00	6EP1322-1LD00	
Product	PSU100D	PSU100D	
Power supply, type	12 V/3 A	12 V/8.3 A	
EMC			
Emitted interference	EN 55022 Class B	EN 55022 Class B	
Supply harmonics limitation	not applicable	EN 61000-3-2	
Noise immunity	EN 61000-6-2	EN 61000-6-2	
perating data			
Ambient temperature			
<ul> <li>during operation</li> </ul>	-10 +70 °C	-10 +70 °C	
- Note	with natural convection	with natural convection	
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	
lechanics			
Connection technology	screw-type terminals	screw-type terminals	
Connections			
Supply input	L, N, PE: 1 screw terminal each for 0.3 1.3 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.3 1.3 mm <sup>2</sup> single-core/finely stranded	
Output	+, -: 1 screw terminal each for 0.3 1.3 mm <sup>2</sup>	+, -: 2 screw terminals each for 0.3 1.3 mm <sup>2</sup>	
Auxiliary	-	-	
Vidth of the enclosure	97 mm	97 mm	
Height of the enclosure	98 mm	158 mm	
Depth of the enclosure	38 mm	38 mm	
Required spacing			
• top	20 mm	20 mm	
bottom	0 mm	0 mm	
left	20 mm	20 mm	
right	20 mm	20 mm	
Veight, approx.	0.37 kg	0.57 kg	
nstallation	Wall mounting	Wall mounting	
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	

#### Article No.

PSU100D 1-phase, 12 V DC/3 A	6EP1321-1LD00
Stabilized power supply 35 W, for wall mounting Input: 100 240 V AC Output: 12 V DC/3 A	
PSU100D 1-phase, 12 V DC/8.3 A	6EP1322-1LD00
Stabilized power supply 100 W, for wall mounting Input: 100 240 V AC Output: 12 V DC/8.3 A	

## Overview



The single-phase PSU100D are switch mode power supplies for direct wall mounting using screws. The flat and rugged aluminum enclosure with IP20 degree of protection can be installed in various orientations and is therefore ideal for installation locations with limited space or for mounting in control cabinets and enclosures without a DIN rail. The low-cost devices meet all the basic requirements for a power supply, typical applications being apparatus, automated equipment and automation solutions.

#### Main product highlights

- 24 V DC/ 2.1 A and 3.1 A, 4.1 A, 6.2 A and 12.5 A
- Compact metal enclosure
- Wide-range input
- Green LED for "24 V OK"
- Certification in accordance with CE and UL
- Adjustable output voltage from 22 to 28 V or from 11 to 14 V for compensating voltage drops
- Temperature range from -10 °C to +70 °C

Article number	6EP1331-1LD00	6EP1332-1LD00	6EP1332-1LD10	6EP1333-1LD00	6EP1334-1LD00
Product	PSU100D	PSU100D	PSU100D	PSU100D	PSU100D
Power supply, type	24 V/2.1 A	24 V/3.1 A	24 V/4.1 A	24 V/6.2 A	24 V/12.5 A
Input		21 001 4			
Input	1-phase AC				
Rated voltage value $V_{\text{in rated}}$	100 240 V				
Voltage range AC	85 264 V				
Wide-range input	Yes	Yes	Yes	Yes	Yes
Mains buffering at <i>I</i> <sub>out rated</sub> , min.	15 ms; at V <sub>in</sub> = 115/230 V				
Rated line frequency 1	50 Hz				
Rated line frequency 2	60 Hz				
Rated line range	47 63 Hz				
Input current					
<ul> <li>at rated input voltage 100 V</li> </ul>	1.1 A	1.5 A	2 A	3.1 A	4 A
<ul> <li>at rated input voltage 240 V</li> </ul>	0.7 A	1 A	1.1 A	2 A	2 A
Switch-on current limiting (+25 °C), max.	60 A	60 A	75 A	75 A	60 A
l²t, max.	1.2 A <sup>2</sup> ·s	1.2 A <sup>2</sup> ·s	4 A <sup>2</sup> ·s	6.5 A <sup>2</sup> ·s	1.1 A <sup>2.</sup> s
Built-in incoming fuse	internal	internal	internal	internal	internal
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 10 A characteristic C or from 16 A characteristic B	Recommended miniature circuit breaker: from 10 A characteristic C or from 16 A characteristic B	Recommended miniature circuit breaker: from 10 A characteristic C or from 16 A characteristic B	Recommended miniature circuit breaker: from 10 A characteristic C or from 16 A characteristic B	Recommended miniature circuit breaker: from 10 A characteristic C or from 16 A characteristic B
Output					
Output	Controlled, isolated DC voltage				
Rated voltage Vout DC	24 V				
Total tolerance, static ±	2 %	2 %	2 %	2 %	2 %
Static mains compensation, approx.	0.5 %	0.5 %	0.5 %	0.5 %	0.5 %
Static load balancing, approx.	1 %	1 %	1 %	1 %	0.5 %
Residual ripple peak-peak, max.	100 mV				
Spikes peak-peak, max. (bandwidth: 20 MHz)	100 mV				
Adjustment range	22 28 V				
Product function Output voltage adjustable	Yes	Yes	Yes	Yes	Yes

Wall mounting

# 1-phase, 24 V DC (PSU100D)

## Technical specifications (continued)

Article number Product	6EP1331-1LD00 PSU100D	6EP1332-1LD00 PSU100D	6EP1332-1LD10 PSU100D	6EP1333-1LD00 PSU100D	6EP1334-1LD00 PSU100D
Power supply, type	24 V/2.1 A	24 V/3.1 A	24 V/4.1 A	24 V/6.2 A	24 V/12.5 A
Output (continued)					
Output voltage setting	via potentiometer	via potentiometer	via potentiometer	via potentiometer	via potentiometer
Status display Signaling	Green LED for 24 V OK	Green LED for 24 V OK	Green LED for 24 V OK	Green LED for 24 V OK	Green LED for 24 V Of
On/off behavior	Overshoot of V <sub>out</sub> < 2 %	Overshoot of $V_{\rm out}$ < 2 %	Overshoot of $V_{\rm out}$ < 2 %	Overshoot of $V_{\rm out}$ < 2 %	Overshoot of $V_{\rm out}$ < 2 %
Startup delay, max.	1 s	2.5 s	1 s	1 s	1 s
Voltage increase time of the output voltage maximum	30 ms	30 ms	30 ms	30 ms	30 ms
Rated current value Iout rated	2.1 A	3.1 A	4.1 A	6.2 A	12.5 A
Current range	0 2.1 A	0 3.1 A	0 4.1 A	0 6.2 A	0 12.5 A
Note	+50 +70 °C: Derating 2.5%/K	+50 +70 °C: Derating 2.5%/K	+50 +70 °C: Derating 2.5%/K	+50 +70 °C: Derating 2.5%/K	+50 +70 °C: Derating 2.5%/K
Supplied active power typical	50 W	75 W	100 W	150 W	300 W
Parallel switching for enhanced performance	Yes	Yes	Yes	Yes	Yes
Numbers of parallel switchable units for enhanced performance	2	2	2	2	2
Efficiency	00.0/	00.0/	00.0/	00.0/	00.0/
Efficiency at $V_{\text{out rated}}$ , $I_{\text{out rated}}$ , approx.	86 %	86 %	86 %	86 %	86 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	8 W	12 W	16 W	24 W	48 W
Closed-loop control	0.5.0/				
Dynamic mains compensation $(V_{\text{in rated}} \pm 15 \%)$ , max.	0.5 %	0.5 %	0.5 %	0.5 %	0.5 %
Dynamic load smoothing $(I_{out}: 50/100/50 \%), U_{out} \pm typ.$	5 %	5 %	5 %	5 %	5 %
Protection and monitoring					
Output overvoltage protection	< 35 V	< 35 V	< 35 V	< 35 V	< 35 V
Current limitation, typ.	2.5 A	3.7 A	4.9 A	7.4 A	15 A
Property of the output Short-circuit proof	Yes	Yes	Yes	Yes	Yes
Short-circuit protection	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart
Enduring short circuit current RMS value					
typical	6 A	6 A	10 A	16 A	15 A
Overload/short-circuit indicator	-	-	-	-	-
Safety					
Primary/secondary isolation Galvanic isolation	Yes Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Yes Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Yes Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Yes Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Yes Safety extra low output voltage V <sub>out</sub> according to EN 60950-1
Protection class	Class I	Class I	Class I	Class I	Class I
Leakage current		010331	010331	010331	010001
maximum	3.5 mA	3.5 mA	3.5 mA	3.5 mA	3.5 mA
• typical	1 mA	1 mA	1 mA	1 mA	1 mA
CE mark	Yes	Yes	Yes	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508,	cULus-Listed (UL 508,	CULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; CURus (UL 60950-1, CSA C22.2 No. 60950-1), File E151273	cULus-Listed (UL 508,	cULus-Listed (UL 508
Explosion protection	-	-	-	-	-
FM approval	-	-	-	-	-
CB approval	Yes	Yes	Yes	Yes	Yes
Marine approval	-	-	-	-	-
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20	IP20
EMC					
Emitted interference	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	not applicable	EN 61000-3-2	EN 61000-3-2	-	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2

Siemens KT 10.1 · 2019/2020

# Special designs, special uses Wall mounting

1-phase, 24 V DC (PSU100D)

Article number	6EP1331-1LD00	6EP1332-1LD00	6EP1332-1LD10	6EP1333-1LD00	6EP1334-1LD00
Product	PSU100D	PSU100D	PSU100D	PSU100D	PSU100D
Power supply, type	24 V/2.1 A	24 V/3.1 A	24 V/4.1 A	24 V/6.2 A	24 V/12.5 A
Operating data					
Ambient temperature					
<ul> <li>during operation</li> </ul>	-10 +70 °C	-10 +70 °C	-10 +70 °C	-10 +70 °C	-10 +70 °C
- Note	with natural convection	with natural convection	with natural convection	with natural convection	with forced convection (ventilator)
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
Mechanics					
Connection technology	screw-type terminals	screw-type terminals	screw-type terminals	screw-type terminals	screw-type terminals
Connections					
Supply input	L, N, PE: 1 screw terminal each for 0.3 1.3 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.3 1.3 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.3 1.3 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.3 1.3 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.5 1.3 mm <sup>2</sup> single-core/finely stranded
Output	+, -: 1 screw terminal each for 0.3 1.3 mm <sup>2</sup>	+, -: 1 screw terminal each for 0.3 1.3 mm <sup>2</sup>	+, -: 2 screw terminals each for 0.3 1.3 mm <sup>2</sup>	+, -: 2 screw terminals each for 0.3 1.3 mm <sup>2</sup>	+, -: 2 screw termina each for 0.5 1.3 m
<ul> <li>Auxiliary</li> </ul>	-	-	-	-	-
Width of the enclosure	97 mm	97 mm	97 mm	97 mm	105 mm
Height of the enclosure	128 mm	128 mm	158 mm	178 mm	199 mm
Depth of the enclosure	38 mm	38 mm	38 mm	38 mm	41 mm
Required spacing					
• top	20 mm	20 mm	20 mm	20 mm	20 mm
• bottom	0 mm	0 mm	0 mm	0 mm	0 mm
• left	20 mm	20 mm	20 mm	20 mm	20 mm
• right	20 mm	20 mm	20 mm	20 mm	20 mm
Weight, approx.	0.35 kg	0.37 kg	0.5 kg	0.55 kg	0.81 kg
Installation	Wall mounting	Wall mounting	Wall mounting	Wall mounting	Wall mounting
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rate input voltage and ambient temperature +25 °C (unless otherwise specified)

#### Ordering data Article No.

PSU100D 1-phase, 24 V DC/2.1 A	6EP1331-1LD00
Stabilized power supply 50 W, for wall mounting Input: 100 240 V AC	
Output: 24 V DC/2.1 A	
PSU100D 1-phase, 24 V DC/3.1 A	6EP1332-1LD00
Stabilized power supply 75 W, for wall mounting Input: 100 240 V AC Output: 24 V DC/3.1 A	
PSU100D 1-phase, 24 V DC/4.1 A	6EP1332-1LD10
Stabilized power supply 100 W, for wall mounting Input: 100 240 V AC Output: 24 V DC/4.1 A	
PSU100D 1-phase, 24 V DC/6.2 A	6EP1333-1LD00
Stabilized power supply 150 W, for wall mounting Input: 100 240 V AC Output: 24 V DC/6.2 A	
PSU100D 1-phase, 24 V DC/12.5 A	6EP1334-1LD00
Stabilized power supply 300 W, for wall mounting Input: 100 240 V AC Output: 24 V DC/12.5 A	

High degree of protection

## 1-phase, 24 V DC (SITOP PSU100P, IP67)

### Overview



The SITOP PSU100P 1-phase power supplies for wall mounting, with their rugged design and IP 67 degree of protection are ideal for distributed applications outside the control cabinet.

#### Main product highlights

- 24 V DC/ 5 A and 8 A
- Automatic switchover of the input voltage
- Temperature range from -25 °C to +60 °C without derating
- High efficiency of 93 % for low internal power consumption
- Isolated relay contact "24 V OK"
- Operation display on the device by means of LED (green = "24 V OK", flashing red = overload)

Article number	6EP1333-7CA00	6EP1334-7CA00
Product	SITOP PSU100P	SITOP PSU100P
Power supply, type	24 V/5 A	24 V/8 A
Input		
Input	1-phase AC	1-phase AC
Note	Automatic range selection	Automatic range selection
Supply voltage		
<ul> <li>1 at AC Rated value</li> </ul>	120 V	120 V
<ul> <li>2 at AC Rated value</li> </ul>	230 V	230 V
Input voltage		
• 1 at AC	85 132 V	85 132 V
• 2 at AC	170 264 V	170 264 V
Wide-range input	No	No
Overvoltage resistance	Implemented internally with varistor	Implemented internally with varistor
Mains buffering at Iout rated, min.	40 ms; at V <sub>in</sub> = 120/230 V	40 ms; at V <sub>in</sub> = 120/230 V
Rated line frequency 1	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz
Input current		
<ul> <li>at rated input voltage 120 V</li> </ul>	2.25 A	3.5 A
<ul> <li>at rated input voltage 230 V</li> </ul>	1.24 A	1.52 A
Switch-on current limiting (+25 °C), max.	15 A	15 A
l²t, max.	0.6 A <sup>2.</sup> s	0.6 A <sup>2</sup> ·s
Built-in incoming fuse	T 3.15 A	T 6.3 A
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 6 A characteristic C/B	Recommended miniature circuit breaker: from 6 A characteristic C/B
Output		
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage Vout DC	24 V	24 V
Total tolerance, static ±	3 %	3 %
Static mains compensation, approx.	0.1 %	0.1 %
Static load balancing, approx.	0.2 %	0.2 %
Residual ripple peak-peak, max.	50 mV	50 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	100 mV	100 mV
Product function Output voltage adjustable	No	No
Status display	Green LED: 24 V OK; red LED flashing: "overload/short-circuit"	Green LED: 24 V OK; red LED flashing: "overload/short-circuit"
Signaling	Relay contact (NO contact, rating 30 V AC/ 0.5 A; 30 V DC/1 A) for 24 V OK	Relay contact (NO contact, rating 30 V AC/ 0.5 A; 30 V DC/1 A) for 24 V OK

# Special designs, special uses High degree of protection

# 1-phase, 24 V DC (SITOP PSU100P, IP67)

Article number	6EP1333-7CA00	6EP1334-7CA00
Product	SITOP PSU100P	SITOP PSU100P
Power supply, type	24 V/5 A	24 V/8 A
Dutput (continued)		
On/off behavior	Overshoot of $V_{out} < 3 \%$	Overshoot of $V_{out} < 3 \%$
Startup delay, max.	1.5 s	1.5 s
Voltage rise, typ.	22 ms	23 ms
Voltage increase time of the output voltage	100 ms	100 ms
maximum	100 113	100 113
Rated current value Iout rated	5 A	8 A
Current range	05A	08A
Supplied active power typical	133 W	206 W
	135 W	200 W
Short-term overload current		
<ul> <li>on short-circuiting during the start-up typical</li> </ul>	20 A	30 A
<ul> <li>at short-circuit during operation typical</li> </ul>	20 A	30 A
Duration of overloading capability for excess current		
<ul> <li>on short-circuiting during the</li> </ul>	50 ms	50 ms
start-up		
<ul> <li>at short-circuit during operation</li> </ul>	50 ms	50 ms
Parallel switching for enhanced performance	Yes; Symmetric wiring required	Yes; Symmetric wiring required
Numbers of parallel switchable units for	2	2
enhanced performance		
Efficiency		
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	90 %	93.6 %
Power loss at $V_{\text{out rated}}$ , $I_{\text{out rated}}$ , approx.	12.9 W	13.1 W
Closed-loop control		
Dynamic mains compensation	0.2 %	0.2 %
$(V_{\text{in rated}} \pm 15 \%)$ , max.	0.2 /0	0.2 /0
Dynamic load smoothing $(I_{out}: 50/100/50 \%), U_{out} \pm typ.$	1 %	1 %
Setting time maximum	2 ms	2 ms
Protection and monitoring		
Output overvoltage protection	< 29 V	< 29 V
Current limitation, typ.	5.5 A	9 A
Property of the output		
Short-circuit proof	Yes	Yes
Short-circuit protection	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart
Enduring short circuit current RMS value		Lieutonic shatdown, automatic restart
•	C A	0.4
• maximum	6 A	9 A
• typical	5 A	8 A
Overload/short-circuit indicator	Red LED flashing for "overload/short-circuit"	Red LED flashing for "overload/short-circuit"
Safety		
Primary/secondary isolation	Yes	Yes
Galvanic isolation	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 609 1 and EN 50178
Protection class	Class I	Class I
Leakage current		
• maximum	3.5 mA	3.5 mA
typical	1 mA	1 mA
CE mark	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1)
	00200 E0100 (02 000, 00h 022.2 NO. 107.1)	00200 Elotod (02 000, 00A 022.2 NO. 107.1)
Explosion protection	·	-
FM approval	-	-
CB approval	No	No
Marine approval	-	-
Degree of protection (EN 60529)	IP67, enclosure type 5 indoor	IP67, enclosure type 5 indoor
EMC		
Emitted interference	EN 55022 Class B	EN 55022 Class B
Emitted interference Supply harmonics limitation	EN 55022 Class B EN 61000-3-2	EN 55022 Class B EN 61000-3-2

# **Special designs, special uses** High degree of protection

# 1-phase, 24 V DC (SITOP PSU100P, IP67)

Article number	6EP1333-7CA00	6EP1334-7CA00
Product	SITOP PSU100P	SITOP PSU100P
Power supply, type	24 V/5 A	24 V/8 A
Operating data		
Ambient temperature		
during operation	-25 +60 °C	-25 +60 °C
- Note	with natural convection	with natural convection
during transport	-40 +85 °C	-40 +85 °C
during storage	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	3K6 without direct sunlight	3K6 without direct sunlight
Mechanics		
Connection technology	screw-type terminals	screw-type terminals
Connections		
Supply input	L1, N, PE: Plug connector 7/8" (counterpart see "Operating Instructions (compact)")	L1, N, PE: Plug connector 7/8" (counterpart see "Operating Instructions (compact)
• Output	+, -: Plug connector 7/8" (counterpart see "Operating Instructions (compact)")	+, -: Plug connector 7/8" (counterpart see "Operating Instructions (compact)
Auxiliary	Alarm signals: M12 plug-in connector 4-pin	Alarm signals: M12 plug-in connector 4-pin
Product function		
<ul> <li>removable terminal at input</li> </ul>	Yes	Yes
<ul> <li>removable terminal at output</li> </ul>	Yes	Yes
Width of the enclosure	120 mm	120 mm
Height of the enclosure	181 mm	181 mm
Depth of the enclosure	60.5 mm	60.5 mm
Required spacing		
• top	50 mm	50 mm
• bottom	0 mm	0 mm
• left	0 mm	0 mm
• right	0 mm	0 mm
Weight, approx.	1.1 kg	1.3 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes
Installation	Wall mounting	Wall mounting
MTBF at 40 °C	1 500 000 h	800 000 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Ordering data	Article No.	More information
SITOP PSU100P 1-phase, 24 V DC/5 A	6EP1333-7CA00	Select the appropriate power supply quickly and easily with the TIA Selection Tool:
Stabilized power supply with IP67 degree of protection Input: 120/230 V AC Output: 24 V DC/5 A		http://www.siemens.com/tst
SITOP PSU100P 1-phase, 24 V DC/8 A	6EP1334-7CA00	
Stabilized power supply with IP67 degree of protection Input: 120/230 V AC Output: 24 V DC/8 A		

## Special designs, special uses High degree of protection

3-phase, 24 V DC (ET200pro PS, IP67)

## Overview



The SIMATIC ET200pro PS power supply unit with degree of pro-tection IP67 is used as the electronics/encoder supply and load voltage supply of the new SIMATIC ET 200pro distributed I/O system for use close to the machine without a cabinet. With a signaling contact for "24 V OK" and "Overtemperature", as well as a second plug-in connector for input voltage loop-through.

Product	SIMATIC ET200pro PS
Power supply, type	24 V/8 A
nput	
Input	3-phase AC
Rated voltage value V <sub>in rated</sub>	400 480 V
Voltage range AC	340 550 V
• Note	320 340 V for max. 1 min
Wide-range input	Yes
Overvoltage resistance	Implemented internally with varistors
Mains buffering at I <sub>out rated</sub> , min.	15 ms; at V <sub>in</sub> = 400 V
Rated line frequency 1	50 Hz
Rated line frequency 2	60 Hz
Rated line range	45 66 Hz
Input current	
<ul> <li>at rated input voltage 400 V</li> </ul>	0.5 A
Switch-on current limiting (+25 °C), max.	40 A
²t, max.	3.5 A <sup>2</sup> ·s
Built-in incoming fuse	T 4 A
Protection in the mains power input (IEC 898)	Required: Circuit breaker 3RV2011-1DA10 or 3RV2711-1DD10 (UL 489)

Article number	6ES7148-4PC00-0HA0
Product	SIMATIC ET200pro PS
Power supply, type	24 V/8 A
Output	
Output	Controlled, isolated DC voltage
Rated voltage Vout DC	24 V
Total tolerance, static ±	3 %
Static mains compensation, approx.	0.5 %
Static load balancing, approx.	0.5 %
Residual ripple peak-peak, max.	200 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	250 mV
Product function Output voltage adjustable	No
Output voltage setting	-
Status display	Green LED for 24 V OK
Signaling	max. 30 V, 10 mA; Power-Good (High-Pegel 1L+ for V <sub>out</sub> in range 21.3 29 V); Overtemperature warning at least 30 s before switch-off (high level 1L+ when the max. internal temperature is exceeded)
On/off behavior	Overshoot of $V_{out} < 2 \%$
Startup delay, max.	1.5 s
Voltage rise, typ.	40 ms
Rated current value Iout rated	8 A
Current range	0 8 A
Supplied active power typical	192 W
Short-term overload current	
<ul> <li>on short-circuiting during the start-up typical</li> </ul>	50 A
<ul> <li>at short-circuit during operation typical</li> </ul>	50 A
Duration of overloading capability for excess current	
<ul> <li>on short-circuiting during the start-up</li> </ul>	100 ms
<ul> <li>at short-circuit during operation</li> </ul>	100 ms
Parallel switching for enhanced performance	No

Article number Product

Power supply, type

## Special designs, special uses

High degree of protection

## 3-phase, 24 V DC (ET200pro PS, IP67)

#### Technical specifications (continued)

····· · · · · · · · · · · · · · · · ·	
Article number	6ES7148-4PC00-0HA0
Product	SIMATIC ET200pro PS
Power supply, type	24 V/8 A
Efficiency	
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	88 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	25 W
Closed-loop control	
Dynamic mains compensation $(V_{\text{in rated}} \pm 15 \%)$ , max.	0.5 %
Dynamic load smoothing ( <i>I</i> <sub>out</sub> : 50/100/50 %), <i>U</i> <sub>out</sub> ± typ.	1 %
Setting time maximum	2 ms
Protection and monitoring	
Output overvoltage protection	< 33 V
Current limitation, typ.	9.4 A
Property of the output Short-circuit proof	Yes
Short-circuit protection	Electronic shutdown, automatic restart
Enduring short circuit current RMS value	
• maximum	10 A
Overload/short-circuit indicator	-
Safety	
Primary/secondary isolation	Yes
Galvanic isolation	Protective extra low output voltage V <sub>out</sub> according to EN 60950-1 and EN 50178
Protection class	Class I
Leakage current	
• maximum	3.5 mA
• typical	0.4 mA
CE mark	Yes
UL/cUL (CSA) approval	UL-Listed (UL 508) according to NFPA compatibility (National Fire Protection Association), see operating instructions
Explosion protection	-
FM approval	-
CB approval	Yes
Marine approval	-

IP67, enclosure type 5 indoor

EMC		
Emitted interference	EN 55022 Class A	
Supply harmonics limitation	-	
Noise immunity	EN 61000-6-2	
Operating data		
Ambient temperature		
<ul> <li>during operation</li> </ul>	-25 +55 °C	
- Note	with natural convection	
<ul> <li>during transport</li> </ul>	-40 +70 °C	
<ul> <li>during storage</li> </ul>	-40 +70 °C	
Humidity class according to EN 60721	Climate class 3K3, no condensation	
Mechanics		
Connection technology	screw-type terminals	
Connections		
Supply input	L1, L2, L3, PE: Plug connector HAN Q4/2 (counterpart see "Electrical accessories")	
• Output	L+, M: 2 x 1.5 mm <sup>2</sup> each (4-pole cable for +/- with open, labeled ends, 4 x 1.5 mm <sup>2</sup> )	
Auxiliary	Alarm signals: M12 plug-in connector 5-pin	
Width of the enclosure	310 mm	
Height of the enclosure	135 mm	
Depth of the enclosure	90 mm	
Weight, approx.	2.8 kg	
Product feature of the enclosure housing for side-by-side mounting	No	
Installation	Can be mounted onto ET200pro mounting rail	
Electrical accessories	Power connector (Input: 3RK1911-2BE30 (6 mm²)) (Output: 3RK1911-2BF10 (4 mm²))	
MTBF at 40 °C	196 354 h	
Other information	Specifications at rated input voltage	

6ES7148-4PC00-0HA0

SIMATIC ET200pro PS

24 V/8 A

Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Degree of protection (EN 60529)

# Special designs, special uses High degree of protection

# 3-phase, 24 V DC (ET200pro PS, IP67)

Ordering data	Article No.	Accessories	Article No.
SIMATIC ET 200pro PS	6ES7148-4PC00-0HA0	Power connector	
Stabilized power supply in distributed I/O system design, permitting the loop-through of energy to further modules; with degree of protection IP67;	For connecting to the distributed I/O system • For X1 (6 mm <sup>2</sup> ) • For X2 (4 mm <sup>2</sup> )	3RK1911-2BE30 3RK1911-2BF10	
Input: 400-480 V 3 AC Output: 24 V DC/8 A		National Fire Protection Association compatible	
		These devices are only approved for installation in industrial machinery according to the NFPA79 Electrical Standard for Industrial Machinery. • for X1 SIMATIC ET200pro PS 61 88 201 1003.xx (AWG10)* • for X1 SITOP PSU300P 61 88 201 1000.xx / 61 88 201 1002.xx (AWG14)* • for X2 SIMATIC ET200pro PS 61 88 202 1010.xx (AWG10)*	* http://www.harting.com
		supplied blanking cap for X2 • for X3 Phoenix-Contact SAC-5P-M12-M12FS	3RK1902-0CK00
		supplied blanking cap for X3	
		Sealing cap	
		For 9-pole power sockets • X2 (1 unit) • X2 (10 units)	3RK1902-0CK00 3RK1902-0CJ00

7

Battery charging

3-phase, 12 V DC

#### Overview



The SITOP PSU3800 3-phase power supplies are suitable for battery charging, thanks to their constant-current characteristic. For other applications, the output characteristic can also be switched to latching shutdown. The three-phase, wide-range input enables them to be used worldwide. The slim design requires little space on the DIN rail. Installation gaps are not required.

Article number	6EP3424-8UB00-0AY0	Article number	6EP3424-8UB00-0AY0
Product	SITOP PSU3800	Product	SITOP PSU3800
Power supply, type	12 V/20 A	Power supply, type	12 V/20 A
Input		Output (continued)	
Input	3-phase AC	Status display	Green LED for 12 V OK
Rated voltage value V <sub>in rated</sub> Voltage range AC	400 500 V 320 575 V	Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for 12 V OK
		On/off behavior	No overshoot of $V_{out}$ (soft start)
Wide-range input	Yes	Startup delay, max.	2.5 s
Mains buffering at I <sub>out rated</sub> , min. Rated line frequency 1	15 ms; at V <sub>in</sub> = 400 V 50 Hz	Voltage increase time of the output voltage maximum	500 ms
Rated line frequency 2	60 Hz	Rated current value I <sub>out rated</sub>	20 A
Rated line range	47 63 Hz	Current range	0 20 A
Input current		Note	+60 +70 °C: Derating 2%/K
<ul> <li>at rated input voltage 400 V</li> </ul>	0.7 A	Supplied active power typical	240 W
<ul> <li>at rated input voltage 500 V</li> </ul>	0.6 A	Constant overload current	240 11
Switch-on current limiting (+25 °C), max.	16 A	<ul> <li>on short-circuiting during the</li> </ul>	22 A
I²t, max.	0.8 A <sup>2</sup> ·s	start-up typical Parallel switching for enhanced	Yes; switchable characteristic
Built-in incoming fuse	none	performance	res, switchable characteristic
Protection in the mains power input (IEC 898)	Required: 3-pole connected miniature circuit breaker 6 16 A	Numbers of parallel switchable units for enhanced performance	2
	characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or	Efficiency	
	3RV2711-1DD10 (UL 489)	Efficiency at Vout rated, Iout rated,	91 %
Dutput		approx.	
Output	Controlled, isolated DC voltage	Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> ,	24 W
Rated voltage V <sub>out</sub> DC	12 V	approx. Closed-loop control	
Total tolerance, static $\pm$	3 %	•	0.1.9/
Static mains compensation, approx.	0.1 %	Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	0.1 %
Static load balancing, approx.	0.2 %	Dynamic load smoothing	1 %
Residual ripple peak-peak, max.	100 mV	$(I_{out}: 50/100/50 \%), U_{out} \pm typ.$	
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV	Load step setting time 50 to 100%, typ.	0.2 ms
Adjustment range	12 14 V	Load step setting time 100 to 50%,	0.2 ms
Product function Output voltage	Yes	typ.	
adjustable Output voltage setting	via potentiometer; max. 240 W	Dynamic load smoothing ( <i>I</i> <sub>out</sub> : 10/90/10 %), <i>U</i> <sub>out</sub> ± typ.	2 %
e alpar tollago oolling		Load step setting time 10 to 90%, typ.	0.2 ms
		Load step setting time 90 to 10%, typ.	0.2 ms
		Setting time maximum	10 ms

# Special designs, special uses Battery charging

3-phase, 12 V DC

Article number	6EP3424-8UB00-0AY0	Article number	6EP3424-8UB00-0AY0
Product	SITOP PSU3800	Product	SITOP PSU3800
Power supply, type	12 V/20 A	Power supply, type	12 V/20 A
Protection and monitoring		Mechanics	
Output overvoltage protection	< 18 V	Connection technology	screw-type terminals
Current limitation, typ.	22 A	Connections	
Property of the output Short-circuit proof	Yes	Supply input	L1, L2, L3, PE: 1 screw terminal ear for 0.2 4 mm <sup>2</sup> single-core/finely
Short-circuit protection	Alternatively, constant current characteristic approx. 22 A or latching shutdown	• Output	stranded +, -: 2 screw terminals each for 0.2 4 mm <sup>2</sup>
Enduring short circuit current RMS value		Auxiliary	13, 14 (alarm signal): 1 screw terminal each for 0.14 1.5 mm <sup>2</sup> ;
typical	22 A		15, 16 (Remote): 1 screw terminal
Overload/short-circuit indicator	LED yellow for "overload", LED red		each for 0.14 1.5 mm <sup>2</sup>
	for "latching shutdown"	Width of the enclosure	70 mm
Safety		Height of the enclosure	125 mm
Primary/secondary isolation	Yes	Depth of the enclosure	125 mm
Galvanic isolation	Safety extra low output voltage Vout	Required spacing	
	according to EN 60950-1	• top	50 mm
Protection class	Class I	• bottom	50 mm
Leakage current		• left	0 mm
• maximum	3.5 mA	• right	0 mm
typical	0.9 mA	Weight, approx.	1.2 kg
CE mark	Yes	Product feature of the enclosure housing for side-by-side mounting	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	Installation	Snaps onto DIN rail EN 60715 35x7.5/15
Explosion protection	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2,	Mechanical accessories	Device identification label 20 mm × 7 mm, pale turquoise 3RT1900-1SB20
	Group ABCD, T4	Other information	Specifications at rated input voltage
FM approval	-		and ambient temperature +25 °C (unless otherwise specified)
CB approval	Yes		(unless otherwise specified)
Marine approval	ABS, DNV GL		
Degree of protection (EN 60529)	IP20	Ordering data	Article No.
EMC	-	SITOP PSU3800, 3-phase,	6EP3424-8UB00-0AY0
Emitted interference	EN 55022 Class B	12 V DC/20 A	0EF3424-00D00-0AT0
Supply harmonics limitation	EN 61000-3-2	Stabilized power supply	
Noise immunity	EN 61000-6-2	Input: 400 500 V 3 AC	
Operating data		Output: 12 V DC/20 A	
Ambient temperature			
during operation	-25 +70 °C	Accessories	Article No.
- Note	with natural convection		
<ul> <li>during transport</li> </ul>	-40 +85 °C	Device identification label	3RT2900-1SB20
<ul> <li>during storage</li> </ul>	-40 +85 °C		
Humidity class according to EN 60721	Climate class 3K3, no condensation		

Battery charging

3-phase, 24 V DC

### Overview



Thanks to their constant-current characteristic, SITOP PSU3800 3-phase power supplies (24 V DC/17 A and 30 A/40 A) are suitable for battery charging, thanks to their constant-current characteristic. For other applications the output characteristic can also be switched to latching shutdown. The three-phase, wide-range input enables them to be used worldwide. The slim design requires little space on the DIN rail. Installation gaps are not required.

Article number	6EP3436-8UB00-0AY0	6EP3437-8UB00-0AY0
Product	SITOP PSU3800	SITOP PSU3800
Power supply, type	24 V/17 A	24 V/30 - 40 A
Input		
Input	3-phase AC	3-phase AC
Rated voltage value V <sub>in rated</sub>	400 500 V	400 500 V
Voltage range AC	320 575 V	320 575 V
Wide-range input	Yes	Yes
Mains buffering at Iout rated, min.	15 ms; at $V_{in} = 400 \text{ V}$	10 ms; at V <sub>in</sub> = 400 V
Rated line frequency 1	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz
Rated line range	47 63 Hz	45 65 Hz
Input current		
<ul> <li>at rated input voltage 400 V</li> </ul>	1.1 A	2.1 A
<ul> <li>at rated input voltage 500 V</li> </ul>	0.9 A	1.7 A
Switch-on current limiting (+25 °C), max.	16 A	13 A
I²t, max.	0.8 A <sup>2.</sup> s	2.24 A <sup>2.</sup> s
Built-in incoming fuse	none	
Protection in the mains power input (IEC 898)	Required: 3-pole connected miniature circuit breaker 6 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)	Required: 3-pole connected miniature circuit breaker 10 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)
Output		
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage Vout DC	24 V	24 V
Total tolerance, static ±	3 %	3 %
Static mains compensation, approx.	0.1 %	0.1 %
Static load balancing, approx.	0.2 %	0.2 %
Residual ripple peak-peak, max.	100 mV	100 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV	240 mV
Adjustment range	24 28 V	24 28 V
Product function Output voltage adjustable	Yes	Yes
Output voltage setting	via potentiometer; max. 480 W	via potentiometer; max. 960 W
Status display	Green LED for 24 V OK	Green LED for 24 V OK
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"

# Special designs, special uses Battery charging

3-phase, 24 V DC

Auticle number		
Article number	6EP3436-8UB00-0AY0	6EP3437-8UB00-0AY0
Product	SITOP PSU3800	
Power supply, type	24 V/17 A	24 V/30 - 40 A
Output (continued)		
On/off behavior	No overshoot of $V_{out}$ (soft start)	minimal overshoot (< 3 %)
Startup delay, max.	2.5 s	0.1 s
Voltage increase time of the output voltage maximum	500 ms	100 ms
Rated current value I <sub>out rated</sub>	17 A	40 A
Current range	0 17 A	0 40 A
• Note	+60 +70 °C: Derating 2%/K	+60 +70 °C: Derating 4%/K
Supplied active power typical Constant overload current	408 W	960 W
<ul> <li>on short-circuiting during the start-up typical</li> </ul>	19 A	48 A
Parallel switching for enhanced performance	Yes; switchable characteristic	Yes; switchable characteristic
Numbers of parallel switchable units for	2	2
enhanced performance		
Efficiency		
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	94 %	94 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx. Power loss [W] during no-load operation	26 W -	66 W 4 W
maximum		
Closed-loop control		
Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	0.1 %	1 %
Dynamic load smoothing ( $I_{out}$ : 50/100/50 %), $U_{out} \pm$ typ.	1 %	3 %
Load step setting time 50 to 100%, typ.	0.2 ms	-
Load step setting time 100 to 50%, typ.	0.2 ms	-
Dynamic load smoothing ( $I_{out}$ : 10/90/10 %), $U_{out} \pm typ$ .	2 %	-
Load step setting time 10 to 90%, typ.	0.2 ms	-
Load step setting time 90 to 10%, typ.	0.2 ms	-
Setting time maximum	10 ms	10 ms
Protection and monitoring		
Output overvoltage protection	< 32 V	< 31.8 V
Current limitation, typ.	19 A	44 A
Property of the output Short-circuit proof	Yes	Yes
Short-circuit protection	Alternatively, constant current characteristic approx. 19 A or latching shutdown	Constant current characteristic approx. 44 A
Enduring short circuit current RMS value		
• typical	19 A	50 A
Overload/short-circuit indicator	LED yellow for "overload", LED red for "latching shutdown"	LED yellow for "overload", LED red for "latching shutdown"
Safety		
Primary/secondary isolation	Yes	Yes
Galvanic isolation	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178
Protection class	Class I	Class I
Leakage current		
• maximum	3.5 mA	1 mA
• typical	0.9 mA	0.6 mA
CE mark	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
Explosion protection	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4	IECEX EX NA NC IIC T4 Gc; ATEX (EX) II 3G EX NA NC IIC T4 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4
FM approval	-	-
CB approval	Yes	Yes
Marine approval	ABS, DNV GL	-
Degree of protection (EN 60529)	IP20	IP20

Battery charging

# 3-phase, 24 V DC

Article number	6EP3436-8UB00-0AY0	6EP3437-8UB00-0AY0
Product	SITOP PSU3800	SITOP PSU3800
Power supply, type	24 V/17 A	24 V/30 - 40 A
EMC		
Emitted interference	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2	EN 61000-3-2
Noise immunity	EN 61000-6-2	EN 61000-6-2
Operating data		
Ambient temperature		
<ul> <li>during operation</li> </ul>	-25 +70 °C	-25 +70 °C
- Note	with natural convection	With natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation
<b>Mechanics</b>		
Connection technology	screw-type terminals	screw-type terminals
Connections		
<ul> <li>Supply input</li> </ul>	L1, L2, L3, PE: 1 screw terminal each for 0.2 4 mm <sup>2</sup> single-core/finely stranded	L1, L2, L3, PE: 1 screw terminal each for 0.5 4 mm <sup>2</sup> single-core/finely stranded
• Output	+, -: 2 screw terminals each for 0.2 4 mm <sup>2</sup>	+: 2 screw terminals each for 0.5 16 mm <sup>2</sup> ; -: 3 screw terminals each for 0.5 16 mm <sup>2</sup>
• Auxiliary	13, 14 (alarm signal): 1 screw terminal each for 0.14 1.5 mm <sup>2</sup> ; 15, 16 (Remote): 1 screw terminal each for 0.14 1.5 mm <sup>2</sup>	13, 14 (alarm signal), 15, 16 (Remote): 1 screw terminal each for 0.05 2.5 mm <sup>2</sup>
Width of the enclosure	70 mm	135 mm
Height of the enclosure	125 mm	145 mm
Depth of the enclosure	125 mm	150 mm
Required spacing		
• top	50 mm	40 mm
• bottom	50 mm	40 mm
• left	0 mm	0 mm
• right	0 mm	0 mm
Weight, approx.	1.2 kg	3.3 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x15
Mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20
MTBF at 40 °C		517 015 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Ordering data	Article No.	Accessories	Article No.
SITOP PSU3800 3-phase, 24 V DC/17 A	6EP3436-8UB00-0AY0	Device identification label	3RT2900-1SB20
Stabilized power supply Input: 400 500 V 3 AC Output: 24 V DC/17 A			
SITOP PSU3800 3-phase, 24 V DC/30/40 A	6EP3437-8UB00-0AY0		
Stabilized power supply Input: 400 500 V 3 AC Output: 24 V DC/30/40 A			

Introduction

## Overview



SITOP PSU2600 for use in medical engineering

The 1-phase and 3-phase stabilized SITOP PSU2600 power supplies are specially designed for use in medical engineering.

#### Main product highlights

- Rugged metal enclosure for industrial use
- High degree of efficiency ensures low heat dissipation
- Adjustable 24 to 28 V output voltage to compensate for voltage drops with long cables
- "Single-fault safe" overvoltage protection on the secondary side (< 32 V) for supplying safety I/O components</li>
- Parallel operation of up to 2 PSUs
- Power Boost with 3 times the rated current for selective tripping of downstream miniature circuit breakers
- Status indicator via LED display (green DC is OK) and signaling contact
- Radio interference suppression Class B according to EN 60601
- Supply harmonics limitation according to EN 61000-3-2
- CE, UL/cUL approval, IEC 60601-1 (MOOP)
- 20 A version enables electronic RESET of 24 V via an isolated input

Medical applications

#### 1-phase, 24 V DC

#### Overview



#### Single-phase power supply for medical engineering

The rugged, 1-phase SITOP PSU2600 power supplies in metal enclosures are specially designed for use in medical engineering. These devices are characterized by a high degree of efficiency and low heat dissipation. The adjustable 24 to 28 V output voltage enables compensation of voltage drops with long cables The overvoltage protection on the secondary side (< 32 V) ensures the supply for the safety I/O components. SITOP PSU2600 power supplies are certified according to CE, UL/cUL and IEC60601-1 (MOOP) and feature radio interference suppression Class B according to EN 60601 as well as supply harmonics limitation according to EN 61000-3-2.

To further increase 24 V availability, the SITOP PSU2600 can be combined with **DC UPS**, **redundancy** and **selectivity** modules.

Article number	6EP4333-0SB00-0AY0
Product	SITOP PSU2600
Power supply, type	24 V/5 A
nput	
Input	1-phase AC or DC
Rated voltage value V <sub>in rated</sub>	120 230 V
Voltage range AC	85 264 V
Supply voltage	
• at DC	110 220 V
Input voltage	
• at DC	88 265 V
Wide-range input	Yes
Mains buffering at I <sub>out rated</sub> , min.	30 ms; at <i>V</i> <sub>in</sub> = 230 V
Rated line frequency 1	50 Hz
Rated line frequency 2	60 Hz
Rated line range	47 63 Hz
Input current	
<ul> <li>at rated input voltage 120 V</li> </ul>	2.5 A
<ul> <li>at rated input voltage 230 V</li> </ul>	1.4 A
Switch-on current limiting (+25 °C),	36 A
max.	
Built-in incoming fuse	3.15 A
Protection in the mains power input (IEC 898)	None required. Fuse protection starting from 6 A Char. C possible
Dutput	starting nom o A onal. o possible
Output	Controlled, isolated DC voltage
Rated voltage V <sub>out</sub> DC	24 V
Total tolerance, static $\pm$	3 %
Static mains compensation, approx.	0.1 %
Static load balancing, approx.	0.2 %
Residual ripple peak-peak, max.	50 mV
Spikes peak-peak, max.	200 mV
(bandwidth: 20 MHz)	200
Adjustment range	24 28.8 V
Product function Output voltage	Yes
adjustable	
Output voltage setting	via potentiometer; max. 120 W

Article number	6EP4333-0SB00-0AY0
Product	SITOP PSU2600
Power supply, type	24 V/5 A
Output (continued)	
Status display	Green LED for 24 V OK
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"
On/off behavior	No overshoot of $V_{out}$ (soft start)
Startup delay, max.	1 s
Voltage increase time of the output voltage maximum	500 ms
Rated current value Iout rated	5 A
Current range	0 5 A
Note	+60 °C
Supplied active power typical	120 W
Constant overload current	
<ul> <li>on short-circuiting during the start-up typical</li> </ul>	6 A
Parallel switching for enhanced performance	No
Efficiency	
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	89 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	15 W
Power loss [W] during no-load operation maximum	1 W
Closed-loop control	
Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	0.1 %
Dynamic load smoothing ( $I_{out}$ : 50/100/50 %), $U_{out} \pm typ$ .	1 %
Load step setting time 50 to 100%, typ.	0.2 ms
Load step setting time 100 to 50%, typ.	0.2 ms
Dynamic load smoothing ( <i>I<sub>out</sub>: 10/90/10 %), U<sub>out</sub> ± typ.</i>	2 %
Load step setting time 10 to 90%, typ.	0.2 ms
Load step setting time 90 to 10%, typ.	0.2 ms
Setting time maximum	10 ms

# Special designs, special uses Medical applications

1-phase, 24 V DC

Article number	6EP4333-0SB00-0AY0	Article number	6EP4333-0SB00-0AY0
Product	SITOP PSU2600	Product	SITOP PSU2600
Power supply, type	24 V/5 A	Power supply, type	24 V/5 A
Protection and monitoring		Mechanics	
Output overvoltage protection	< 32 V	Connection technology	screw-type terminals
Current limitation, typ.	6 A	Connections	
Property of the output Short-circuit proof	Yes	Supply input	L1, N, PE: 1 screw terminal each fo 0.2 2.5 mm <sup>2</sup> single-core/finely
Short-circuit protection	Shutdown and periodic restart attempts	• Output	stranded +, -: 2 screw terminals each for 0.2 2.5 mm <sup>2</sup>
Enduring short circuit current RMS value		Auxiliary	13, 14 (alarm signal): 1 screw terminal each for 0.05 2.5 mm <sup>2</sup>
typical	6 A	Width of the enclosure	42 mm
Safety			42 mm
Primary/secondary isolation	Yes	Height of the enclosure Depth of the enclosure	125 mm
Galvanic isolation	Safety extra low output voltage V <sub>out</sub> according to EN 60950-1	Required spacing	12511111
Protection class	Class I	• top	50 mm
Leakage current		bottom	50 mm
• maximum	3.5 mA	• left	0 mm
typical	1.1 mA	• right	0 mm
CE mark	Yes	Weight, approx.	0.6 kg
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	Product feature of the enclosure housing for side-by-side mounting	Yes
Explosion protection	-	Installation	Snaps onto DIN rail
FM approval	-		EN 60715 35x7.5/15
CB approval	Yes	Other information	Specifications at rated input voltag and ambient temperature +25 °C
Marine approval	-		(unless otherwise specified)
Degree of protection (EN 60529)	IP20		,
EMC		Ordering date	
Emitted interference	EN 55022 Class B	Ordering data	Article No.
Supply harmonics limitation	EN 61000-3-2	SITOP PSU2600 1-phase,	6EP4333-0SB00-0AY0
Noise immunity	EN 61000-6-2	24 V DC/5 A	
Operating data		Stabilized power supply	
Ambient temperature		Input: 120 230 V AC Output: 24 V DC/5 A	
<ul> <li>during operation</li> </ul>	0 60 °C	Ouipul. 24 V DO/3 A	
- Note	with natural convection		
<ul> <li>during transport</li> </ul>	-40 +85 °C	Accessories	
<ul> <li>during storage</li> </ul>	-40 +85 °C		
Humidity class according to	Climate class 3K3, no condensation	SITOP redundancy modules	see page 9/6
EN 60721		SITOP selectivity modules	see page 9/14

7

Medical applications

#### 3-phase, 24 V DC

#### Overview



#### Three-phase power supply for medical engineering

The rugged, 3-phase SITOP PSU2600 power supplies in metal enclosures are specially designed for use in medical engineering. These devices are characterized by a high degree of efficiency and low heat dissipation. The adjustable 24 to 28 V output voltage enables compensation of voltage drops with long cables The overvoltage protection on the secondary side (< 32 V) ensures the supply for the safety I/O components. SITOP PSU2600 power supplies are certified according to CE, UL/cUL and IEC60601-1 (MOOP) and feature radio interference suppression Class B according to EN 60601 as well as supply harmonics limitation according to EN 61000-3-2.

To further increase 24 V availability, the SITOP PSU2600 can be combined with **DC UPS**, **redundancy** and **selectivity** modules.

#### Technical specifications

Article number	6EP4436-0SB00-0AY0	Article number	6EP4436-0SB00-0AY0
Product	SITOP PSU2600	Product	SITOP PSU2600
Power supply, type	24 V/20 A	Power supply, type	24 V/20 A
Input		Output (continued)	
Input	3-phase AC	Signaling	Relay contact (NO contact,
Rated voltage value V <sub>in rated</sub>	400 500 V	On left behavior	rating 60 V DC/ 0.3 A) for "24 V OK"
Voltage range AC	340 575 V	On/off behavior	No overshoot of $V_{out}$ (soft start)
Wide-range input	Yes	Startup delay, max.	2.5 s
Mains buffering at I <sub>out rated</sub> , min.	15 ms; at V <sub>in</sub> = 400 V	Voltage increase time of the output voltage maximum	500 ms
Rated line frequency 1	50 Hz	Rated current value I <sub>out rated</sub>	20 A
Rated line frequency 2	60 Hz	Current range	0 20 A
Rated line range	47 63 Hz	Note	+60 °C
Input current		Supplied active power typical	480 W
<ul> <li>at rated input voltage 400 V</li> </ul>	1.2 A	Short-term overload current	460 W
<ul> <li>at rated input voltage 500 V</li> </ul>	1 A	at short-circuit during operation	60 A
Switch-on current limiting (+25 °C), max.	16 A	typical	00 A
I²t, max.	0.8 A <sup>2</sup> ·s	Duration of overloading capability for excess current	
Built-in incoming fuse	none	<ul> <li>at short-circuit during operation</li> </ul>	25 ms
Protection in the mains power input	Required: 3-pole connected	Constant overload current	
(IEC 898)	miniature circuit breaker 6 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A),	<ul> <li>on short-circuiting during the start-up typical</li> </ul>	23 A
	3RV2021-1HA (setting 8 A) or 3RV2711-1DD10 (UL 489)	Parallel switching for enhanced performance	Yes
Dutput		Numbers of parallel switchable units	2
Output	Controlled, isolated DC voltage	for enhanced performance	
Rated voltage V <sub>out</sub> DC	24 V	Efficiency	
Total tolerance, static $\pm$	2 %	Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	93 %
Static mains compensation, approx.	1 %	Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> ,	36 W
Static load balancing, approx.	0.2 %	approx.	
Residual ripple peak-peak, max.	50 mV	Power loss [W] during no-load	4 W
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV	operation maximum Closed-loop control	
Adjustment range	24 28.8 V	Dynamic mains compensation	0.1 %
Product function Output voltage adjustable	Yes	(V <sub>in rated</sub> ±15 %), max. Dynamic load smoothing	2 %
Output voltage setting	via potentiometer; max. 480 W	$(I_{out}: 50/100/50 \%), U_{out} \pm typ.$	
Status display	Green LED for 24 V OK	Load step setting time 50 to 100%, typ.	0.2 ms
		Load step setting time 100 to 50%, typ.	0.2 ms
		Dynamic load smoothing $(1 + 10/90/10\%)$	3 %

(I<sub>out</sub>: 10/90/10 %), U<sub>out</sub> ± typ.

3-phase, 24 V DC

Article number	6EP4436-0SB00-0AY0
Product	SITOP PSU2600
Power supply, type	24 V/20 A
Closed-loop control (continued)	
Load step setting time 10 to 90%, typ	o. 0.2 ms
Load step setting time 90 to 10%, typ	o. 0.2 ms
Setting time maximum	10 ms
Protection and monitoring	
Output overvoltage protection	< 32 V
Current limitation, typ.	23 A
Property of the output	Yes
Short-circuit proof	
Short-circuit protection	Constant current characteristic approx. 23 A
Enduring short circuit current	
RMS value	
typical	23 A
Safety	
Primary/secondary isolation	Yes
Galvanic isolation	Safety extra low output voltage $V_{\rm out}$ according to EN 60950-1
Protection class	Class I
Leakage current	
• maximum	3.5 mA
typical	1.7 mA
CE mark	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
Explosion protection	-
FM approval	-
CB approval	Yes
Marine approval	-
Degree of protection (EN 60529)	IP20
EMC	EN EFRON OL
Emitted interference	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2
Noise immunity	EN 61000-6-2
Operating data	
Ambient temperature	0 60 °C
during operation	
- Note	with natural convection -40 +85 °C
<ul><li>during transport</li><li>during storage</li></ul>	-40 +85 °C
Humidity class according to	Climate class 3K3, no condensation
EN 60721	Climate class 5(3, 10 condensation
Mechanics	
Connection technology	screw-type terminals
Connections	
Supply input	L1, L2, L3, PE: 1 screw terminal each for 0.2 4 mm <sup>2</sup> single-core/finely stranded
Output	+, -: 2 screw terminals each for 0.2 4 mm <sup>2</sup>
Auxiliary	Signal and remote: 1 screw terminal each for 0.14 1.5 mm <sup>2</sup>
Width of the enclosure	90 mm
Height of the enclosure	125 mm
Depth of the enclosure	125 mm

Article number	6EP4436-0SB00-0AY0
Product	SITOP PSU2600
Power supply, type	24 V/20 A
Mechanics (continued)	
Required spacing	
• top	50 mm
bottom	50 mm
• left	0 mm
• right	0 mm
Weight, approx.	1.3 kg
Product feature of the enclosure housing for side-by-side mounting	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
Ordering data	Article No.
SITOP PSU2600, 3-phase, 24 V DC/20 A	6EP4436-0SB00-0AY0
Stabilized power supply Input: 400 500 V 3 AC Output: 24 V DC/20 A	
Accessories	A
Arrasentias	Article No.
Accessones	
SITOP redundancy modules	see page 9/6
	see page 9/6 see page 9/14

Alternative output voltages

## 1-phase, 2 x 15 V DC (SITOP PSU3600 dual)

### Overview



#### Technical specifications

Article number Product	6EP3323-0SA00-0BY0 SITOP PSU3600 dual
Power supply, type	2 x 15 V/3.5 A
Input	
Input	1-phase AC or DC
Rated voltage value Vin rated	120 230 V
Voltage range AC	85 264 V
Note	Derating at < 110 V AC/DC: output power max. 100 W
Input voltage	
• at DC	88 250 V
Wide-range input	Yes
Mains buffering at I <sub>out rated</sub> , min.	10 ms; at V <sub>in</sub> = 120 V, 40 ms at V <sub>in</sub> = 187 V
Rated line frequency 1	50 Hz
Rated line frequency 2	60 Hz
Rated line range	47 63 Hz
Input current	
<ul> <li>at rated input voltage 120 V</li> </ul>	2.2 A
<ul> <li>at rated input voltage 230 V</li> </ul>	1.3 A
<ul> <li>at rated input voltage 110 V</li> </ul>	1.3 A
<ul> <li>at rated input voltage 220 V</li> </ul>	0.7 A
Switch-on current limiting (+25 °C), max.	35 A
l²t, max.	1 A <sup>2</sup> ·s
Built-in incoming fuse	T 3.15 A (not accessible)
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: 6-10 A characteristic C

#### Two power supplies in one compact device

The SITOP PSU3600 single-phase power supply dual was designed as a two-voltage power supply with two independent outputs in order to allow electronic loads to be supplied with both a positive and negative voltage at the same time. If the two potential-free outputs are connected in series, a positive and negative supply voltage of e.g. ±15 V can be generated.

Or you can leave the independent outputs separate and supply different loads with different nominal voltages, e.g. 24 V and 15 V, with only a single power supply unit due to the wide adjust-ment range of the output voltage from 12 V to 28 V for each output.

In addition, both outputs are power limited according to NEC Class 2, opening up further application possibilities.

Article number	6EP3323-0SA00-0BY0
Product	SITOP PSU3600 dual
Power supply, type Output	2 x 15 V/3.5 A
•	Controlled, isolated DC voltage
Output	, 0
Number of outputs	2
Rated voltage V <sub>out</sub> DC	15 V
Output voltage	2 x 15 V DC
at output 1 at DC Rated value	15 V
<ul> <li>at output 2 at DC Rated value</li> </ul>	15 V
Total tolerance, static ±	1 %
Static mains compensation, approx.	0.1 %
Static load balancing, approx.	1 %
Residual ripple peak-peak, max.	50 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	150 mV
Adjustment range	12 28 V
Product function Output voltage adjustable	Yes
Status display	Green LED grün for <i>V</i> <sub>out</sub> >10 V (summation display)
Signaling	-
On/off behavior	Overshoot of $V_{out} < 1 \%$
Startup delay, max.	0.5 s
Rated current value Iout rated	3.5 A
Output current	
<ul> <li>at output 1 Rated value</li> </ul>	3.5 A
at output 2 Rated value	3.5 A
Current range	0 3.5 A
Supplied active power typical	105 W
Parallel switching for enhanced performance	Yes
Numbers of parallel switchable units for enhanced performance	2

Alternative output voltages

# 1-phase, 2 x 15 V DC (SITOP PSU3600 dual)

Article number	6EP3323-0SA00-0BY0
Product	SITOP PSU3600 dual
Power supply, type	2 x 15 V/3.5 A
Efficiency	
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	88 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	18 W
Protection and monitoring	
Output overvoltage protection	≤ 35 V
Current limitation	5 A
Property of the output Short-circuit proof	Yes
Short-circuit protection	Electronic shutdown, automatic restart
Overload/short-circuit indicator	-
Safety	
Primary/secondary isolation	Yes
Galvanic isolation	Safety extra low output voltage $V_{\rm or}$ according to EN 60950-1
Protection class	Class I
Leakage current	
• maximum	3.5 mA
CE mark	Yes
Explosion protection	-
FM approval	-
CB approval	No
Marine approval	-
Degree of protection (EN 60529)	IP20
EMC	
Emitted interference	EN 55022 Class B
	EN 01000 0 0
Supply harmonics limitation	EN 61000-3-2

Article number	6EP3323-0SA00-0BY0
Product	SITOP PSU3600 dual
Power supply, type	2 x 15 V/3.5 A
Operating data	
Ambient temperature	
<ul> <li>during operation</li> </ul>	-25 +70 °C
- Note	Derating > 60°C: 2%/°K
<ul> <li>during transport</li> </ul>	-40 +70 °C
<ul> <li>during storage</li> </ul>	-40 +70 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation
Mechanics	
Connection technology	screw-type terminals
Connections	
Supply input	L1, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded
Output	+: 1 screw terminal per output for 0.5 2.5 mm <sup>2</sup> ; -: 2 screw terminals per output for 0.5 2.5 mm <sup>2</sup>
Auxiliary	-
Width of the enclosure	42 mm
Height of the enclosure	125 mm
Depth of the enclosure	125 mm
Required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
Weight, approx.	0.55 kg
Product feature of the enclosure housing for side-by-side mounting	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Ordering data	Article No.
SITOP PSU3600 dual	6EP3323-0SA00-0BY0
Stabilized power supply Input: 120 230 V AC Output: 2 x 15 V DC/3.5 A	

Alternative output voltages

### 1-phase, 3-52 V DC (SITOP PSU3600 flexi)

#### Overview



# Unlimited variety thanks to variable output—the standard device for different output voltages

What to do if, for example, you need a power supply unit for 5 V, one for 15 V—and then one for 38.5 V as well? Install a special power supply every time?

SITOP PSU3600 power supply is the clever solution in this case! The output voltage can be flexibly adjusted between 3 and 52 V, with a maximum output power of 120 W. The current limitation can also be set between 2 and 10 A. Since you now only need one standard device for multiple applications, you save a lot of time in procurement and avoid costs for logistics and service.

But conventional use as a power supply is not the only conceivable application. The possibility of dynamically changing the output voltage during operation along with numerous additional functions open up a wide range of potential uses.

#### Technical specifications

Article number	6EP3343-0SA00-0AY0	Article number	6EP3343-0SA00-0AY0
Product	SITOP PSU3600 flexi	Product	SITOP PSU3600 flexi
Power supply, type	3-52 V/10 A, 120 W	Power supply, type	3-52 V/10 A, 120 W
nput		Output	
Input	1-phase AC or DC	Output	Controlled, isolated DC voltage
Rated voltage value $V_{in rated}$	120 230 V	Rated voltage Vout DC	24 V
Voltage range AC	85 264 V	Output voltage	3-52 V DC
• Note	Derating at < 110 V AC/DC:	Total tolerance, static ±	1 %
	output power max. 100 W	Static mains compensation, approx.	0.1 %
Supply voltage		Static load balancing, approx.	1 %
<ul> <li>at DC</li> <li>Input voltage</li> </ul>	110 220 V	Sense line connection max. voltage control per line	0.5 V
at DC	88 250 V	Residual ripple peak-peak, max.	50 mV
Wide-range input	Yes	Spikes peak-peak, max.	100 mV
Mains buffering at $I_{out rated}$ , min.	80 ms; With Pa = 120 W and	(bandwidth: 20 MHz)	
S Outraled,	U <sub>e</sub> = 230 V AC	Adjustment range	0 52 V
Rated line frequency 1	50 Hz	Product function	Yes
Rated line frequency 2	60 Hz	Output voltage adjustable	
Rated line range	47 63 Hz	Status display	Two-color LED: green for 24 V OK red for overload
nput current	2.6 A	Signaling	DC OK via relay contact,
• at rated input voltage 120 V			current monitor signal 0 2.5 V
at rated input voltage 230 V	1.3 A	On/off behavior	No overshoot of V <sub>out</sub> (soft start)
at rated input voltage 110 V	1.3 A	Startup delay, max.	0.5 s
at rated input voltage 220 V	0.7 A	Voltage rise, typ.	20 ms
Switch-on current limiting (+25 °C), nax.	35 A	Rated current value Iout rated	10 A
<sup>2</sup> t, max.	1 A <sup>2</sup> ·s	Current range	0 10 A
Built-in incoming fuse	T 3.15 A (not accessible)	Note	Output power max. 120 W
•	Recommended miniature circuit	Supplied active power typical	120 W
Protection in the mains power input IEC 898)	breaker: 6-10 A characteristic C	Constant overload current	
,		<ul> <li>on short-circuiting during the start-up typical</li> </ul>	12 A
		<ul> <li>at short-circuit during operation typical</li> </ul>	12 A
		Parallel switching for enhanced	Yes

performance

Numbers of parallel switchable units

for enhanced performance

2

Alternative output voltages

#### 1-phase, 3-52 V DC (SITOP PSU3600 flexi)

Article number	6EP3343-0SA00-0AY0	Article nur
Product	SITOP PSU3600 flexi	Product
Power supply, type	3-52 V/10 A, 120 W	Power sup
Efficiency		EMC
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> ,	88 %	Emitted inte
approx.	16 W	Supply har
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	16 W	Noise immu
Power loss [W] during no-load operation maximum	3 W	Operating of Ambient ter
Closed-loop control		<ul> <li>during op</li> </ul>
Dynamic mains compensation	0.3 %	- Note
(V <sub>in rated</sub> ±15 %), max.		<ul> <li>during tra</li> </ul>
Dynamic load smoothing ( <i>I</i> <sub>out</sub> : 50/100/50 %), <i>U</i> <sub>out</sub> ± typ.	5 %	<ul> <li>during store</li> </ul>
Setting time maximum	0.2 ms	Humidity cl EN 60721
Protection and monitoring		Mechanics
Output overvoltage protection	≤ 60 V according to EN 60950-1	Connection
Current limitation	2 10 A	Connection
Current limitation	Can be set with potentiometer or analog control voltage signal 0.5 2.5 V	<ul> <li>Supply in</li> </ul>
Property of the output Short-circuit proof	Yes	Output
Short-circuit protection	Electronic current limiting (2 10 A) in the range 3 12 V or power limiting (120 W) in the range 12 52 V	Auxiliary
Enduring short circuit current RMS value		Width of the
• maximum	12 A	Height of th
Safety		Depth of th
Primary/secondary isolation	Yes	Required s
Galvanic isolation	Safety extra low output voltage $V_{out}$ according to EN 60950-1	• top
Protection class	Class I	<ul> <li>bottom</li> </ul>
Leakage current		<ul> <li>left</li> <li>right</li> </ul>
• maximum	3.5 mA	<ul> <li>right</li> <li>Weight, application</li> </ul>
CE mark	Yes	Product fea
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	housing for
Explosion protection	-	Installation
FM approval	-	MTBF at 40
CB approval	Yes	Other inforr
Marine approval	-	
Degree of protection (EN 60529)	IP20	

Technical specifications (continued)

Article number	6EP3343-0SA00-0AY0	
Product	SITOP PSU3600 flexi	
Power supply, type	3-52 V/10 A, 120 W	
EMC		
Emitted interference	EN 55022 Class B	
Supply harmonics limitation	EN 61000-3-2	
Noise immunity	EN 61000-6-2	
Operating data		
Ambient temperature		
<ul> <li>during operation</li> </ul>	-25 +70 °C	
- Note	Derating > 60°C: 2%/°K	
<ul> <li>during transport</li> </ul>	-40 +85 °C	
<ul> <li>during storage</li> </ul>	-40 +85 °C	
Humidity class according to EN 60721	Climate class 3K3, no condensation	
Mechanics		
Connection technology	screw-type terminals	
Connections		
Supply input	L1, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	
• Output	+, -: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	
Auxiliary	Alarm signals, control inputs: screw-type terminals for 0.14 1.5 mm <sup>2</sup> single-core/finely stranded	
Width of the enclosure	42 mm	
Height of the enclosure	125 mm	
Depth of the enclosure	125 mm	
Required spacing		
• top	50 mm	
• bottom	50 mm	
• left	0 mm	
• right	0 mm	
Weight, approx.	0.55 kg	
Product feature of the enclosure housing for side-by-side mounting	Yes	
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	
MTBF at 40 °C	1 200 000 h	
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	
Ordering data	Article No.	

# Ordering data

#### SITOP PSU3600 flexi

Stabilized power supply Input: 120 ... 230 V AC Output: 3 ... 52 V DC / 2 ... 10 A, 120 W

6EP3343-0SA00-0AY0

Special uses

#### 1-phase, 24 V DC

#### Overview



The 24 V/5 A and 10 A power supplies in a compact metal enclosure can be accommodated where only limited installation depth is available. For example, in covered machine supports or hinged frames.

Article number	6EP1333-1AL12	6EP1334-1AL12
Product	SITOP power	SITOP power
Power supply, type	24 V/5 A	24 V/10 A
Input	1 phase AC	1 phase AC
Input	1-phase AC	1-phase AC
• Note	Set by means of selector switch on the device	Set by means of selector switch on the device
Supply voltage	100.1/	400.17
• 1 at AC Rated value	120 V	120 V
• 2 at AC Rated value	230 V	230 V
Input voltage		
• 1 at AC	85 132 V	85 132 V
• 2 at AC	170 264 V	170 264 V
Wide-range input	No	No
Overvoltage resistance	$2.3 \times V_{\text{in rated}}$ , 1.3 ms	$2.3 \times V_{\text{in rated}}$ , 1.3 ms
Mains buffering at I <sub>out rated</sub> , min.	20 ms; at V <sub>in</sub> = 93/187 V	20 ms; at V <sub>in</sub> = 93/187 V
Rated line frequency 1	50 Hz	50 Hz
Rated line frequency 2	60 Hz	60 Hz
Rated line range	47 63 Hz	47 63 Hz
Input current		
<ul> <li>at rated input voltage 120 V</li> </ul>	2.2 A	4 A
<ul> <li>at rated input voltage 230 V</li> </ul>	1.2 A	2.5 A
Switch-on current limiting (+25 °C), max.	32 A	65 A
Duration of inrush current limiting at 25 °C		
• maximum	3 ms	3 ms
I²t, max.	0.8 A <sup>2</sup> ·s	3.3 A <sup>2.</sup> s
Built-in incoming fuse	T 3,15 A/250 V (not accessible)	T 6.3 A/250 V (not accessible)
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 6 A characteristic C	Recommended miniature circuit breaker: from 10 A characteristic C
Output		
Output	Controlled, isolated DC voltage	Controlled, isolated DC voltage
Rated voltage V <sub>out</sub> DC	24 V	24 V
Total tolerance, static $\pm$	1 %	1 %
Static mains compensation, approx.	0.1 %	0.1 %
Static load balancing, approx.	0.5 %	0.5 %
Residual ripple peak-peak, max.	150 mV	150 mV
Residual ripple peak-peak, typ.	40 mV	50 mV

# Special designs, special uses Special uses

1-phase, 24 V DC

rechnical specifications (cont		
Article number	6EP1333-1AL12	6EP1334-1AL12
Product	SITOP power	SITOP power
Power supply, type	24 V/5 A	24 V/10 A
Output (continued)		
Spikes peak-peak, max. (bandwidth: 20 MHz)	240 mV	240 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	100 mV	200 mV
Adjustment range	22 29 V	22 29 V
Product function Output voltage adjustable	Yes	Yes
Output voltage setting	via potentiometer	via potentiometer
Status display	Green LED for 24 V OK	Green LED for 24 V OK
On/off behavior	No overshoot of V <sub>out</sub> (soft start)	No overshoot of V <sub>out</sub> (soft start)
Startup delay, max.	2 s	2 s
Voltage rise, typ.	40 ms	40 ms
Rated current value Iout rated	5 A	10 A
Current range	0 5 A	0 10 A
Supplied active power typical Short-term overload current	120 W	240 W
<ul> <li>on short-circuiting during the start-up typical</li> </ul>	20 A	35 A
<ul> <li>at short-circuit during operation typical</li> </ul>	20 A	35 A
Duration of overloading capability for excess current		
<ul> <li>on short-circuiting during the start-up</li> </ul>	500 ms	700 ms
<ul> <li>at short-circuit during operation</li> </ul>	500 ms	700 ms
Parallel switching for enhanced performance	Yes	Yes
Numbers of parallel switchable units for enhanced performance	2	2
Efficiency		
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	88 %	89 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	17 W	30 W
Closed-loop control		
Dynamic mains compensation $(V_{\text{in rated}} \pm 15 \%)$ , max.	0.3 %	0.3 %
Dynamic load smoothing ( <i>I</i> <sub>out</sub> : 50/100/50 %), <i>U</i> <sub>out</sub> ± typ.	0.5 %	0.6 %
Load step setting time 50 to 100%, typ.	0.1 ms	0.1 ms
Load step setting time 100 to 50%, typ.	0.1 ms	0.2 ms
Protection and monitoring	Additional control loop, shutdown at approve 22.14	Additional control loop, chutdown at approve 22.1/
Output overvoltage protection	Additional control loop, shutdown at approx. 33 V, automatic restart	Additional control loop, shutdown at approx. 33 V, automatic restart
Current limitation	5.5 6.5 A	11 13 A
Property of the output Short-circuit proof	Yes	Yes
Short-circuit protection	Electronic shutdown, automatic restart	Electronic shutdown, automatic restart
Enduring short circuit current RMS value		
• maximum	5 A	10 A
Overload/short-circuit indicator	-	-
Safety		
Primary/secondary isolation	Yes	Yes
Galvanic isolation	Safety extra-low output voltage $U_{\rm out}{\rm acc.}$ to EN 60950-1 and EN 50178	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178
Protection class	Class I	Class I
Leakage current		
• maximum	3.5 mA	3.5 mA
• typical	0.26 mA	0.27 mA

Technical specifications (continued)

Special uses

## 1-phase, 24 V DC

Technical specifications	(continued)
--------------------------	-------------

Article number	6EP1333-1AL12	6EP1334-1AL12
Product	SITOP power	SITOP power
Power supply, type	24 V/5 A	24 V/10 A
Safety (continued)		
CE mark	Yes	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
Explosion protection	-	
FM approval	-	-
CB approval	No	No
Marine approval	-	-
Degree of protection (EN 60529)	IP20	IP20
EMC		
Emitted interference	EN 55022 Class B	EN 55022 Class B
Supply harmonics limitation	-	-
Noise immunity	EN 61000-6-2	EN 61000-6-2
Operating data		
Ambient temperature		
during operation	0 60 °C	0 60 °C
- Note	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C
during storage	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics		
Connection technology	screw-type terminals	screw-type terminals
Connections		
Supply input	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded
Output	L+, M: 3 screw terminals each for 0.5 2.5 mm <sup>2</sup>	L+, M: 3 screw terminals each for 0.5 2.5 mm <sup>2</sup>
Auxiliary	-	-
Width of the enclosure	160 mm	160 mm
Height of the enclosure	130 mm	130 mm
Depth of the enclosure	60 mm	60 mm
Required spacing		
• top	50 mm	50 mm
• bottom	50 mm	50 mm
• left	0 mm	0 mm
• right	0 mm	0 mm
Weight, approx.	0.6 kg	0.72 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
MTBF at 40 °C	1 250 000 h	1 176 471 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Ordering data	Article No.	Accessories	Article No.
SITOP power 1-phase,	6EP1333-1AL12	SITOP power mounting bracket	6EP1971-1AA01
24 V DC/5 A Special Line stabilized power supply Input: 120 230 V AC Output: 24 V DC/5 A		90 degree 35 mm DIN rail, M5 fixing screws, for Special Line flat	
SITOP power 1-phase, 24 V DC/10 A	6EP1334-1AL12		
Special Line Stabilized power supply Input: 120 230 V AC Output: 24 V DC/10 A			

## Special designs, special uses Special uses

1-phase, 48 V DC (SITOP PSU100E)

## Overview



This power supply is optimized for 48 V industrial applications with a focus on single-series and special-purpose machines in the manufacturing industry with power demands up to 5 A. Thanks to the higher voltage of 48 V (instead of 24 V), the same amount of power can be used to achieve a higher performance – even over longer distances. Examples include low-cost machines for cost-efficient switching of valves and magnets, tool systems with electric controls instead of compressed air supplies, supplies for 48 V DC motors or devices which are connected with long cables.

## Technical specifications

Article number	6EP3344-0SB00-0AY0	
Power supply, type	48 V/5 A	
Input		
Input	1-phase AC	
Supply voltage		
<ul> <li>1 at AC Rated value</li> </ul>	100 V	
<ul> <li>2 at AC Rated value</li> </ul>	230 V	
Input voltage		
• 1 at AC	85 132 V	
• 2 at AC	170 264 V	
Wide-range input	No	
Mains buffering at Iout rated, min.	30 ms; at V <sub>in</sub> = 120/230 V	
Rated line frequency 1	50 Hz	
Rated line frequency 2	60 Hz	
Rated line range	47 63 Hz	
Input current		
<ul> <li>at rated input voltage 120 V</li> </ul>	4.4 A	
<ul> <li>at rated input voltage 230 V</li> </ul>	2 A	
Switch-on current limiting (+25 °C), max.	58 A	
I²t, max.	1.5 A <sup>2.</sup> s	
Built-in incoming fuse	T 6.3 A (not accessible), soldered	
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 10 A characteristic C	

Article number	6EP3344-0SB00-0AY0
Power supply, type	48 V/5 A
Output	
Output	Controlled, isolated DC voltage
Rated voltage Vout DC	48 V
Total tolerance, static ±	3 %
Static mains compensation, approx.	0.2 %
Static load balancing, approx.	0.5 %
Residual ripple peak-peak, max.	50 mV
Residual ripple peak-peak, typ.	30 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	150 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	100 mV
Adjustment range	48 54 V
Product function Output voltage adjustable	Yes
Output voltage setting	via potentiometer; max. 240 W
Status display	Green LED for 48 V OK
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for 48 V OK
On/off behavior	Overshoot of Vout approx. 2 %
Startup delay, max.	1.5 s
Voltage rise, typ.	15 ms
Voltage increase time of the output voltage maximum	500 ms
Rated current value Iout rated	5 A
Current range	0 5 A
Note	+60 +70 °C: Derating 5%/K
Supplied active power typical	240 W
Parallel switching for enhanced performance	Yes
Numbers of parallel switchable units for enhanced performance	2

Special uses

## 1-phase, 48 V DC (SITOP PSU100E)

Technical specifications (continued)		
Article number	6EP3344-0SB00-0AY0	
Power supply, type	48 V/5 A	
Efficiency		
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	92 %	
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	12 W	
Closed-loop control		
Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	0.3 %	
Dynamic load smoothing ( $I_{out}$ : 10/90/10 %), $U_{out} \pm typ$ .	1 %	
Load step setting time 10 to 90%, typ.	0.5 ms	
Load step setting time 90 to 10%, typ.	0.5 ms	
Setting time maximum	1 ms	
Protection and monitoring		
Output overvoltage protection	< 60 V	
Current limitation, typ.	5.3 A	
Property of the output Short-circuit proof	Yes	
Short-circuit protection	Electronic shutdown, automatic restart	
Enduring short circuit current RMS value		
typical	8.7 A	
Safety		
Primary/secondary isolation	Yes	
Galvanic isolation	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178	
Protection class	Class I	
Leakage current		
• maximum	3.5 mA	
typical	1 mA	
CE mark	Yes	
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	
Explosion protection	-	
FM approval	-	
CB approval	No	
Marine approval	-	
Degree of protection (EN 60529)	IP20	

Article number	6EP3344-0SB00-0AY0	
Power supply, type	48 V/5 A	
EMC		
Emitted interference	EN 61000-6-4	
Supply harmonics limitation	EN 61000-3-2	
Noise immunity	EN 61000-6-2	
Operating data		
Ambient temperature		
during operation	-25 +70 °C	
- Note	with natural convection	
during transport	-40 +85 °C	
<ul> <li>during storage</li> </ul>	-40 +85 °C	
Humidity class according to EN 60721	Climate class 3K3, no condensation	
Mechanics		
Connection technology	screw-type terminals	
Connections		
Supply input	L, N, PE: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	
• Output	+, -: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup>	
Auxiliary	13, 14 (alarm signal): 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>	
Width of the enclosure	42 mm	
Height of the enclosure	125 mm	
Depth of the enclosure	125 mm	
Required spacing		
• top	50 mm	
bottom	50 mm	
• left	0 mm	
• right	0 mm	
Weight, approx.	0.5 kg	
Product feature of the enclosure housing for side-by-side mounting	Yes	
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	
MTBF at 40 °C	1 050 000 h	
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	
Ordering data	Article No.	
SITOP PSU100E 1-phase,	6EP3344-0SB00-0AY0	

Ordering data	Article No.
SITOP PSU100E 1-phase, 48 V DC/5 A	6EP3344-0SB00-0AY0
Stabilized power supply Input: 120/230 V AC Output: 48 V DC/5 A	

## Accessories

SITOP redundancy modules RED1200

see page 9/6

#### 3-phase, 24 V DC (SITOP PSU300E)

## Overview



## Slimline 3-phase power supply for low power ratings

The SITOP PSU300E 3-phase power supply is designed with a 5 A output current for 24 V applications with low power requirements. The metal enclosure is only 42 mm wide and does not require any lateral gap to other devices on the DIN rail. This is made possible by the low heat dissipation (90% efficiency). The wide-range input from 320 V to 550 V AC permits mains buffering times of 50 ms and thus allows the supply to be used in unstable three-phase networks, thanks to UL certification also in North America. The removable plug-in terminals simplify the AC and DC connection.

#### Technical specifications

Article number	6EP1433-0AA00	Article number	6EP1433-0AA00
Product	SITOP PSU300E	Product	SITOP PSU300E
Power supply, type	24 V/5 A	Power supply, type	24 V/5 A
Input		Output	
Input	3-phase AC	Output	Controlled, isolated DC voltage
Rated voltage value Vin rated	400 500 V	Rated voltage Vout DC	24 V
Voltage range AC	320 550 V	Total tolerance, static ±	3 %
Wide-range input	Yes	Static mains compensation, approx.	3 %
Mains buffering at Iout rated, min.	50 ms; at V <sub>in</sub> = 400 V	Static load balancing, approx.	3 %
Rated line frequency 1	50 Hz	Residual ripple peak-peak, max.	150 mV
Rated line frequency 2	60 Hz	Residual ripple peak-peak, typ.	35 mV
Rated line range Input current	47 63 Hz	Spikes peak-peak, max. (bandwidth: 20 MHz)	240 mV
• at rated input voltage 400 V	0.36 A	Spikes peak-peak, typ. (bandwidth: 20 MHz)	70 mV
<ul> <li>at rated input voltage 500 V</li> </ul>	0.29 A	Adjustment range	24 29 V
Switch-on current limiting (+25 °C), max.	15 A	Product function Output voltage adjustable	Yes
l²t, max.	0.9 A <sup>2</sup> ·s	Output voltage setting	via potentiometer; max. 120 W
Built-in incoming fuse	none	Status display	Green LED for 24 V OK
Protection in the mains power input (IEC 898)	Required: 3-pole connected miniature circuit breaker 6 A characteristic B or C or	Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"
	circuit breaker 3RV2011-1DA10	On/off behavior	Overshoot of Vout approx. 3 %
	(setting 3 A) or 3RV2711-1DD10	Startup delay, max.	0.5 s
	(UL 489)	Voltage rise, typ.	10 ms
		Voltage increase time of the output voltage maximum	100 ms
		Rated current value <i>I</i> out rated	5 A
		Current range	0 5 A
		Supplied active power typical	120 W
		Short-term overload current	
		<ul> <li>on short-circuiting during the start-up typical</li> </ul>	33 A
		<ul> <li>at short-circuit during operation</li> </ul>	28 A

Parallel switching for enhanced performance

No

Special uses

## 3-phase, 24 V DC (SITOP PSU300E)

Technical specifications (continued)		
Article number	6EP1433-0AA00	
Product	SITOP PSU300E	
Power supply, type	24 V/5 A	
Efficiency		
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	90 %	
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	13 W	
Closed-loop control		
Dynamic mains compensation (V <sub>in rated</sub> ±15 %), max.	3 %	
Dynamic load smoothing ( $I_{out}$ : 50/100/50 %), $U_{out} \pm typ$ .	5 %	
Load step setting time 50 to 100%, typ.	1 ms	
Load step setting time 100 to 50%, typ.	1 ms	
Dynamic load smoothing (I <sub>out</sub> : 10/90/10 %), U <sub>out</sub> ± typ.	1 %	
Load step setting time 10 to 90%, typ.	1 ms	
Load step setting time 90 to 10%, typ.	1 ms	
Setting time maximum	30 ms	
Protection and monitoring		
Output overvoltage protection	Yes, according to EN 60950-1	
Current limitation, typ.	11 A	
Property of the output Short-circuit proof	Yes	
Short-circuit protection	Electronic shutdown, automatic restart	
Enduring short circuit current RMS value		
• maximum	7.5 A	
Safety		
Primary/secondary isolation	Yes	
Galvanic isolation	Safety extra-low output voltage $U_{\rm out}$ acc. to EN 60950-1 and EN 50178	
Protection class	Class I	
CE mark	Yes	
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	
Explosion protection	-	
FM approval	-	
CB approval	No	
Marine approval	-	

Autiala mumban	CED1400.04400
Article number	6EP1433-0AA00
Product	SITOP PSU300E
Power supply, type EMC	24 V/5 A
Emitted interference	EN 55022 Class A
Supply harmonics limitation	EN 61000-3-2
Noise immunity	EN 61000-3-2 EN 61000-6-2
Operating data	LIN 01000-0-2
Ambient temperature	
during operation	0 60 °C
- Note	with natural convection
during transport	-40 +85 °C
during storage	-40 +85 °C
Humidity class according to	Climate class 3K3, no condensation
EN 60721	
Mechanics	
Connection technology	screw-type terminals
Connections	
Supply input	L1, L2, L3, PE: Removable screw terminal for 0.5 2.5 mm <sup>2</sup> single-core/finely stranded
Output	+, -: 2 screw terminals each for 0.5 2.5 mm <sup>2</sup>
Auxiliary	13, 14 (alarm signal): 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>
Product function	
<ul> <li>removable terminal at input</li> </ul>	Yes
<ul> <li>removable terminal at output</li> </ul>	Yes
Width of the enclosure	42 mm
Height of the enclosure	125 mm
Depth of the enclosure	125 mm
Required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
Weight, approx.	0.6 kg
Product feature of the enclosure housing for side-by-side mounting	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15
MTBF at 40 °C	2 389 441 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Ordering data	Article No.
SITOP PSU300E 3-phase, 24 V/5 A DC	6EP1433-0AA00
Stabilized power supply Input: 400 500 V 3 AC Output: 24 V DC/5 A	

## Accessories

SITOP redundancy modules	see page 9/6
SITOP selectivity modules	see page 9/14

## Special designs, special uses SIPLUS power supplies

Introduction

## Overview



Particularly harsh industrial environments demand products with special characteristics - products that are more rugged than standard products.

Siemens offers the perfect answer to these requirements with SIPLUS extreme.

SIPLUS product variants are based on the SITOP, LOGO!Power standard power supplies and the power supplies for SIMATIC S7 and expansion modules, and feature the following characteristics:

- Extended ambient temperature range (e.g. -40 ... +70 °C) and conformal coating as protection against extreme and difficult conditions and contact with substances
- DIN EN 50155:

Conforms with standard for electronic equipment used on rolling stock (EN 50155, temperature T1, category)

Ambient conditions			
Conformal coating	Coating of the printed circuit boards and the electronic components		
Technical specifications	The technical data of the standard product applies except for the ambient conditions.		
Relative humidity	100%, condensation/frost permissible. No commissioning in bedewed state.		
Biologically active substances, compliance with EN 60721-3-3	Class 3B2 mold and fungal spores (excluding fauna). The supplied plug covers must remain in place over the unused interfaces during operation!		
Chemically active substances, compliance with EN 60721-3-3	Class 3C4 incl. salt mist in accordance with EN60068-2-52 (degree of severity 3). The supplied plug covers must remain in place over the unused interfaces during operation!		
Mechanically active substances, compliance with EN 60721-3-3	Class 3S4 incl. sand, dust. The supplied plug covers must remain in place over the unused interfaces during operation!		
Air pressure (depending on the highest positive temperature range specified)	1080795 hPa (-1000 +2000 m) see ambient temperature range 795 658 hPa (+2000 +3500 m) derating 10 K 658 540 hPa (+3500 +5000 m) derating 20 K		

For further technical specifications, see the standard products, or visit http://www.siemens.com/siplus-extreme

# **Special designs, special uses** SIPLUS power supplies

## Ordering data

7

Ordering data	Article No.		Article No.	
SIPLUS LOGO!Power		SIPLUS in SIMATIC design		
SIPLUS LOGO!Power 24 V 1.3 A	6AG1331-6SB00-7AY0	For industrial applications with par	ticularly demanding ambient	
Input 100 240 V AC Output 24 V DC, 1.3 A		conditions SIPLUS S7-300 PS 305 6AG1305-1BA80-2AA0		
Extended temperature range		Input: 24 110 V DC	0AG1505-10A00-2AA0	
and exposure to environmental substances		Output: 24 V DC/2 A		
SIPLUS LOGO!Power 24 V 2.5 A	6AG1332-6SB00-7AY0	Extended temperature range and exposure to media		
Input 100 240 V AC		SIPLUS S7-300 PS 307 5 A	6AG1307-1EA01-7AA0	
Output 24 V DC, 2.5 A		Incl. connection bracket 120/230 V AC; 24 V DC		
Extended temperature range and exposure to environmental substances		Output current 5 A (dimensions 60 x 125 x 120)		
SIPLUS LOGO!Power 24 V 4 A	6AG1333-6SB00-7AY0	Extended temperature range and exposure to media		
Input 100 240 V AC Output 24 V DC, 4 A		SIPLUS S7-300 PS 307 10 A	6AG1307-1KA02-7AA0	
Extended temperature range		Incl. connection bracket		
and exposure to environmental substances		120/230 V AC; 24 V DC Output current 10 A (dimensions 80 x 125 x 120)		
SIPLUS smart		Extended temperature range and		
SIPLUS PSU100S 24 V/10 A	6401224 28420 4440	exposure to media		
Stabilized power supply Input: 120/230 V AC Output: 24 V DC/10 A	6AG1334-2BA20-4AA0	SIPLUS S7-1200 PM 1207 power supply		
Extended temperature range and media exposure		Input 120/230 V AC, output 24 V DC, 2.5 A; derating from +55 °C to +70 °C to		
SIPLUS PSU300S 3-phase,	6AG1436-2BA10-7AA0	1.2 A output current		
24 V DC/20 A		• Ambient temperature -25 +70 °C	6AG1332-1SH71-7AA0	
Stabilized power supply Input: 3 AC 400 500 V		• Ambient temperature 0 +60 °C	6AG1332-1SH71-4AA0	
Output: 24 V DC/20 A Extended temperature range and		Extended temperature range and exposure to media		
exposure to environmental		SIPLUS S7-1500 PM 1507		
substances SIPLUS modular		Input 120/230 V AC		
SIPLUS Modular SIPLUS Modular 40 A		Output 24 V DC, 3 A	6AG1332-4BA00-7AA0	
Stabilized power supply		Output 24 V DC, 8 A	6AG1333-4BA00-7AA0	
Input: 120/230 V AC Output: 24 V DC/40 A		Extended temperature range and medial exposure		
<ul> <li>Loading of media</li> </ul>	6AG1337-3BA00-4AA0	SIPLUS S7-1500 system power supply		
• Extended temperature range and exposure to media	6AG1337-3BA00-7AA0	For supplying the backplane bus of the S7-1500 controller		
SIPLUS PS PSU200M 1-phase and 2-phase, 24 V DC/5 A		<ul> <li>24 V DC input voltage, power 25 W</li> </ul>	6AG1505-0KA00-7AB0	
Stabilized power supply Input: 120 230 V/230 500 V AC		<ul> <li>24/48/60 V DC input voltage, power 60 W</li> </ul>	6AG1505-0RA00-7AB0	
• Output: 24 V DC/5 A	6AG1333-3BA10-7AA0	<ul> <li>120/230 V AC input voltage,</li> </ul>	6AG1507-0RA00-7AB0	
• Output: 24 V DC / 10 A	6AG1334-3BA10-7AA0	power 60 W		
Exposure to media		Extended temperature range and exposure to media		
SIPLUS PS PSU8200 3-phase,	6AG1437-3BA10-7AA0	For rolling stock railway application	ns	
DC 24 V/40 A		SIPLUS S7-300 PS 305	6AG1305-1BA80-2AA0	
Stabilized power supply Input: 400 500 V 3 AC Output: 24 V DC / 40 A		Input: 24 … 110 V DC Output: 24 V DC/2 A		
Exposure to media		Conforms to EN 50155		
		Extended temperature range and exposure to media		

# Special designs, special uses SIPLUS power supplies

Ordering data

Ordering data	Article No.		Article No.	
SIPLUS DC/DC converter		SIPLUS modular buffer module	6AG1961-3BA01-7AA0	
SIPLUS PS 24V/0.375A	6AG1931-2BA00-3AA0	For 6AG1 961-3BA01-7AA0;		
DC/DC stabilized power supply Input: 48 220 V DC		buffer time 100 ms to 10 s, dependent on load current		
Output: 24 V DC/0.375 A condensation permissible		SIPLUS PS signaling module modular	6AG1961-3BA10-7AA0	
Medial exposure		For 6AG1XXX-3BA00 -XXXX		
SIPLUS add-on modules		signaling contacts: Output voltage ok,		
SIPLUS PS E202U redundancy module		operational availability ok, remote ON/OFF		
Input/output: 24 V DC/40 A suitable for decoupling two	le for decoupling two power supplies with a um of 20 A output current nded temperature range and ial exposure	Extended temperature range and exposure to media		
SITOP power supplies with a maximum of 20 A output current		SIPLUS signaling module	6AG1961-3BA10-6AA0	
<ul> <li>Extended temperature range and medial exposure</li> </ul>		Hard gold-plated contacts; for 6AG1XXX-3BA00 -XXXX signaling contacts:		
Medial exposure		Output voltage ok,		
SIPLUS PSE200U 3 A	6AG1961-2BA31-7AA0	operational availability ok, remote ON/OFF		
4-channel selectivity module		SIPLUS DC UPS, uninterruptible power supplies		
Input: 24 V AC Output: 24 V DC/3A per channel		SIPLUS PS DC UPS module 15 A	6AG1931-2EC21-2AA0	
output current adjustable 0.5 3 A		Uninterruptible power supply without interface:		
For environmental stress		input: 24 V DC/16 A,		
SIPLUS PSE200U 10 A	6AG1961-2BA41-7AA0	output: 24 V DC/15 A		
4-channel selectivity module		Extended temperature range and medial exposure		
Input: 24 V AC Output: 24 V DC/10 A per channel		SIPLUS PS DC UPS module 40 A	6AG1931-2FC21-7AA0	
output current adjustable 3 10 A		Uninterruptible power supply without interface:		
For environmental stress		input 24 V DC/43 A, output 24 V DC/40 A		
		Extended temperature range and medial exposure		

AS-Interface power supply units

## 1-phase / 1-2-phase / DC, AS-i 30 V (with data decoupling)

## Overview



AS-Interface power supply unit for 3 A

AS-Interface power supply units feed 30 V DC into the AS-Interface cable and supply the AS-Interface components. They contain performance-optimized data decoupling for separating communication signals and supply voltage. As the result, AS-Interface is able to convey both data and power along a single line. The power packs are overload and short-circuit proof.

#### Dimensions

AS-Interface power supply units have compact dimensions in widths of 50 / 70 / 120 mm. No lateral installation clearances to other devices required.

#### Features

- Higher rating: The power supply units deliver currents of 2.6 to 8 A.
- Integrated data decoupling: As the result, AS-Interface is able to convey both data and power along a single line.
- Integrated ground-fault detection: The power supply units perform the reliable detection and signaling of ground faults according to IEC 60204-1. The AS-Interface voltage can be disconnected automatically in the event of a ground fault.
- Integrated overload detection: An output overload is identified and signalized over a diagnostics LED.
- Diagnostics memory: Any ground faults or overloads on the output side are stored in a diagnostics memory until the device is RESET.
- Remote RESET and remote signaling: A ground fault can be signalized and evaluated by relay contacts over a central control and/or indicator light.
- Diagnostics LEDs: Three different LEDs indicate the status of the AS-Interface power supply locally at the power supply unit.
- Ultra-wide input range / 2-phase connection: The ultra-wide input range of 120 to 500 V of the 8 A version means that the supply units can be used in virtually any network worldwide. In addition, this version dispenses with the need for an N conductor as the device can be connected directly between 2 phases of a network.
- Operation with 24 V DC: The 3 A power supply unit is also available as a version with a 24 V DC input. This power supply unit is suitable for use in battery-operated plants or plants with uninterrupted power supply (UPS).
- Removable terminal blocks in spring-type connection: The power supply units are equipped with three removable terminal blocks for simple device replacement: for the input side, for the output side and for Signal/RESET connections.

#### Benefits

- Complete solution for supplying AS-Interface networks while making full use of the maximum possible cable length per AS-i segment
- Only AS-i masters and AS-i slaves need to be connected to the AS-Interface cable to operate AS-Interface
- Compact, room-saving footprint
- Reliable power supply even for large numbers of AS-Interface modules with high power requirements
- Increased safety and savings on additional components owing to the integrated ground fault and overload detection
- Fast fault detection and reduced downtimes thanks to diagnostics memory, remote signaling and remote RESET
- Reduced downtimes as the result of removable terminal blocks which enable the fast exchanging of devices
- Ultra-wide input range of the 8 A version permits single-phase and two-phase operation and removes the need for an N conductor
- Can be used world-wide thanks to, for example, UL/CSA approval (UL 508)
- With the 2.6 A version, the output power is restricted to max. 100 W for use in Class 2 circuits in accordance with NEC (National Electrical Code)

## Ordering data Article No.

#### AS-Interface power supply units, IP20

- AS-i single output 30 V DC
- With integrated ground-fault detection
- With spring-type terminals, removable terminalsAmbient temperature during
- operation -10 ... +70 °C • 2.6 A version with output power restricted to max. 100 W (for Class 2 circuits in accordance with NEC)

Dimensions: Width: 50 mm (2.6 A / 3 A), 70 mm (5 A), 120 mm (8 A); Heinht: 125 mm: Denth: 125 mm

Height: 125 mm; Depth: 125 mm	
Output current: 3 A Input voltage: 120 / 230 V AC (selectable)	3RX9501-0BA00
Output current: 5 A Input voltage: 120 / 230 V AC (selectable)	3RX9502-0BA00
Output current: 8 A Input voltage: 120 / 230 500 V AC (selectable)	3RX9503-0BA00
For special uses	
Output current: 3 A Input voltage: 24 V DC	3RX9501-1BA00
Output current: 2.6 A / max. 100 W Input voltage: 120 / 230 V AC (selectable)	3RX9501-2BA00

#### More information

Operating instructions for AS-i power supply units, see https://support.industry.siemens.com/cs/ww/en/view/21489904 and

https://support.industry.siemens.com/cs/ww/en/view/22317836

Additional components (AS-i masters, AS-i slaves, system accessories) and more information on AS-Interface, see Catalog IC 10, Chapter 2 "Industrial Communication" or Industry Mall https://mall.industry.siemens.com/mall/en/WW/Catalog/ Products/8200016?tree=CatalogTree

AS-Interface power supply units

1-phase, 30 V DC (without data decoupling)

# 

#### PSN130S 30 V power supply units for 3 A, 4 A and 8 A

The PSN130S 30 V power supplies feed 30 V DC into the AS-Interface cable and supply the AS-Interface components, but do not include data decoupling. Additional data decoupling units are needed to separate communication signals and supply voltage, see "S22.5 Data Decoupling Modules" or "DCM 1271 Data Decoupling Module", see Accessories, page 7/42.

The power supplies are overload and short-circuit proof.

#### Dimensions

The 30 V power supply units have compact dimensions in widths of 50 and 70 mm. No lateral installation clearances to other devices required.

#### Features

- Primary-clocked power supplies for connecting to a singlephase AC power supply system
- Power for currents of 3 A, 4 A and 8 A
- The output voltage is floating, and resistant to short-circuits and no-load operation. In the event of an overload, the output voltage will be reduced or switched off. After a short-circuit or overload the devices will start up again automatically.
- In the event of a device fault, the output voltage will be limited to max. 37 V.
- Modular installation devices in degree of protection IP20 and safety class I
- Diagnostics: With an output voltage > 26.5 V DC, the green LED (30V OK) is lit and the signaling contact 13-14 is closed.

#### Benefits

- Low-cost alternative solution for supplying AS-Interface networks while making full use of the maximum possible cable length per AS-i segment
- · Cost advantage particularly for multiple networks
- Compact, space-saving dimensions
- Reliable power supply even for large numbers of AS-Interface modules with high power requirements
- Can be used worldwide thanks to, for example, UL/CSA approval (UL 508)

## Application



Accessories: Data decoupling modules S22.5 and DCM 1271

A data decoupling module is additionally required in order to use a PSN130S 30 V power supply unit for AS-Interface.

With the aid of the data decoupling module, the AS-Interface network can be supplied with 30 V DC from a standard power supply unit and the transmission of data and power can be realized along one cable.


Alternatively, it is also possible to use a standard 24 V DC power supply unit (AS-i Power24V). However, in this case please note that all components involved must be designed for the reduced voltage and that the maximum length of an AS-i Power24V network is limited to 50 m.

The power supply units must comply with the PELV (Protective Extra Low Voltage) or SELV (Safety Extra Low Voltage) standards, have a residual ripple of < 250 mVpp and in the event of a fault, must limit the output voltage to a maximum of 40 V.

The combination of data decoupling modules and standard power supply units is therefore a cost-efficient alternative to the service-proven AS-Interface power supply units.

The quality of the data signals and the reliable operation of the AS-i network are not negatively affected as the result.

## Configuration examples of AS-Interface networks with a 30 V power supply unit




Configuration of AS-Interface multiple networks, each with one PSN130S 30 V power supply unit (examples with schematic representation): Double network based on S22.5 double data decoupling module and SIMATIC ET 200SP with two CM AS-i Master ST modules

Overview

AS-Interface power supply units

## 1-phase, 30 V DC (without data decoupling)

### Application (continued)



Configuration of AS-Interface multiple networks, with one PSN130S 30 V power supply unit (examples with schematic representation): Triple network based on SIMATIC S7-1200 with DCM 1271 data decoupling modules and CM 1243-2 communication processors

#### Technical specifications

-					
Product		PSN130S			
Version		power su 3 A	ipply uni 4 A	t 8 A	
Input data		37	77	0.4	
<ul> <li>Input data</li> <li>Input voltage, rated value U<sub>e</sub></li> </ul>	V AC	120 / 230 automatic			
<ul> <li>Input voltage range</li> </ul>	V AC	85 132			
Mains frequency	Hz	50 / 60			
Power consumption at full load, typ.	W	103	139	270	
Output data		00			
<ul> <li>Output voltage, rated value U<sub>a</sub></li> <li>Residual ripple</li> </ul>	V DC mV <sub>ss</sub>	30 < 150			
Output current, rated value	A	3	4	8	
at -20 +60 °C					
Max. output current	А	3	3	4	
at +60 +70 °C					
<ul> <li>Degree of efficiency in rated condit</li> <li>Degree of efficiency</li> </ul>	www.wons	87	88	90	
<ul> <li>Power loss, typ.</li> </ul>	Ŵ	12	17	25	
Protection and monitoring					
<ul> <li>Output overvoltage protection</li> </ul>	V	< 37			
<ul> <li>Current limit, typ.</li> </ul>	А	4	5,5	11	
Safety		Output voltage PELV / SELV according to IEC 60950			
<ul> <li>Electrical separation primary / secondary</li> </ul>					
plinary, cocorradiy		and EN 5			
Protection class		1			
Degree of protection		IP20			
Approvals <ul> <li>UL</li> </ul>		UL 508 / 0	<u></u>	,	
Pollution degree		IEC 6095			
<ul> <li>Overvoltage category and</li> </ul>			EN 50178 and IEC 61558		
electrical separation					
EMC					
<ul> <li>Emitted interference (class B)</li> <li>Line harmonics limit</li> </ul>		IEC 6100			
<ul> <li>Interference immunity</li> </ul>		IEC 6100			
Operating data					
Ambient temperature					
Operation	°C	-20 +70			
Transport / storage	°C	-40 +85 2	5		
Pollution degree Humidity class		2 Climate c	lass		
Fidmidity class		according		50010,	
		relative ai			
<u> </u>		100 %, wi	itnout cor	ndensation	
<ul> <li>Dimensions and weight</li> <li>Width</li> </ul>	mm	50	50	70	
<ul> <li>Height x depth</li> </ul>	mm	125 x 126		10	
Weight	kg	0.4	0.4	0.7	
-	-				

Ordering data	Article No.
PSN130S 30 V DC power supply units (without AS-i data decoupling)	
Output voltage 30 V DC, with screw terminals,	
Dimensions: Width: 50 mm (3 A / 4 A), 70 mm (8 A); Height: 125 mm; Depth: 126.5 mm	
Output current: 3 A Input voltage:120 / 230 V AC (automatic selection)	3RX9511-0AA00
Output current: 4 A Input voltage: 120 / 230 V AC (automatic selection)	3RX9512-0AA00
Output current: 8 A Input voltage: 120 / 230 V AC (automatic selection)	3RX9513-0AA00

Accessories

Article No.

Data decoupling modules in enclosure, 22.5 mm

S22.5 data decoupling modules	
With screw terminals, removable terminals, Dimensions: Width: 22.5 mm; Height: 101 mm; Depth: 115 mm	
<ul> <li>Single data decoupling module, 1 x 4 A</li> </ul>	3RK1901-1DE12-1AA0
Double data decoupling module, 2 x 4 A	3RK1901-1DE22-1AA0
With spring-type terminals, removable terminals, Dimensions: Width: 22.5 mm; Height: 105 mm; Depth: 115 mm	
<ul> <li>Single data decoupling module, 1 x 4 A</li> </ul>	3RK1901-1DG12-1AA0
Double data decoupling module, 2 x 4 A	3RK1901-1DG22-1AA0
Data decoupling modules in enclosu	ure for S7-1200
DCM 1271 data decoupling module	3RK7271-1AA30-0AA0

3RK7271-1AA30-0AA0
3RK1901-3MA00
3RK1901-3MB00

#### More information

For operating instructions and other technical information see http://support.automation.siemens.com/WW/view/en/64364000 and

https://support.industry.siemens.com/cs/ww/en/view/44030789.

Additional components (AS-i masters, AS-i slaves, system accessories) and more information on AS-Interface, see Catalog IC 10, Chapter 2 "Industrial Communication" or Industry Mall https://mall.industry.siemens.com/mall/en/WW/Catalog/ Products/8200016?tree=CatalogTree © Siemens 2019

## SITOP DC UPS uninterruptible power supplies





8/2	Introduction		
8/3	DC UPS with capacitors		
8/10	DC UPS with battery modules		
8/10	SITOP UPS1600 DC UPS modules		
8/18	SITOP UPS1100 battery modules		
8/22	SITOP DC UPS		
8/28	DC UPS battery modules		

## Introduction

## Overview



SITOP offers a comprehensive portfolio to protect against power failures with durations from a few seconds to several hours, ranging from buffer modules to system-integrated DC UPS units. Selection is based on the energy storage unit used, the associated ambient conditions, performance and functionality.

The selection matrix should help you to find the right 24 V buffering for your application:

SITOP modules for 24 V buffering	Buffer module <sup>1) 2)</sup>	DC-UPS with capacitors	SITOP UPS1600 DC-UPS modules/SITOP UPS1100 battery modules	SITOP DC UPS		
Energy storage units						
24 V buffering up to	10 s	Minutes	Hours	Hours		
Storage medium	Electrolytic capacitors	Double-layer capacitors	Lead-gel batteries, rechargeable lithium iron phosphate batteries	Lead-gel batteries		
Battery lifetime dependent on temperature. The specified time refers to a fall to 50 % of the original capacity in the case of lead batteries and 80 % in the case of capacitors.	0 +50 °C: > 8 years	0 +50 °C: > 8 years	+20 +40 °C: 4 1 years (high-temperature rechargeable battery: +20 +60 °C: >10 1 years) (LiFePo: +20° +40 °C: 15 9 years)	+20 +40 °C: 4 1 years (high-temperature rechargeable battery: +20 +60 °C: > 10 1 years)		
Operating temperature range of battery	0 +60 °C	0 +60 °C	-15° +60 °C (high-temperature rechargeable battery: -40° +60 °C)	-15° +50 °C (high-temperature rechargeable battery: -40° +60 °C)		
Ventilation required		-	<ul> <li>(Lead gel)</li> <li>(Lithium iron phosphate)</li> </ul>	•		
UPS module/electronics						
Max. rated output current	40 A	15 A	40 A	40 A		
Max. dynamic overload current	40 A (200 ms)	25 A (200 ms)	120 A (30 ms) / 60 A (5 s/min)	56 A (80 ms)		
Interfaces		I/O, USB	I/O, USB, OPC UA, Ethernet/ PROFINET	I/O, serial, USB		
Information about operation and diagnostics via						
Signaling contact	-	•	•	•		
<ul><li>OPC servers</li><li>Web server</li></ul>	-	•		•		
OPC UA server	-	-	•	-		
<ul> <li>S7 function blocks</li> </ul>	-	-	•	-		
Library for SIMATIC PCS 7	-	-	•	-		
WinCC faceplate	-	-	•	-		
Shutdown of multiple PCs/ PLCs	-	-	•	-		
Starting from the battery, without supply voltage (stand-alone mode)	-	-	•	-		
Engineering via • Software tool (PC) • TIA Portal • SIMATIC STEP 7 • SIMATIC PCS 7	- - -	•	:	•		
Degree of protection	IP20	IP20	IP20	IP20		

<sup>1)</sup> for SITOP smart and SITOP modular power supply units

<sup>2)</sup> Technical specifications can be found under "Add-on modules/Buffer modules"

## More information

The TIA Selection Tool offers detailed selection guidance according to criteria such as the required buffer time, load current or peak current: http://www.siemens.com/tst

## SITOP DC UPS uninterruptible power supplies DC UPS with capacitors

DC UPS with capacitors

## Overview



SITOP 24 V power supplies can be expanded with a SITOP UPS500 uninterruptible DC power supply (DC UPS) for bridging short-term power failures in the order of minutes. In PC-based automation solutions, the highly capacitive double-layer capacitors of the SITOP UPS500 supply enough energy to safeguard operating and application data and close software applications in a defined manner. You can increase the buffer times using SITOP PSU501S expansion modules (up to 3).


#### Benefits

- 24 V buffering for a few minutes to allow data to be backed up and applications to be closed.
- · Absolutely maintenance-free
- Long lifetime, even at high temperatures
- High ambient temperatures up to +60 °C
- · Short charging times
- No ventilation is required since no gas is emitted
- Distributed applications possible without control cabinet
- Software tool, free of charge, for easy configuring and integrating in PC-based systems

## Application

The high-capacitance double-layer capacitors bridge power failures for a few minutes. The time is normally sufficient, for example, for the safe shutdown of PC-based automation systems. The USB interface and a free software tool enable easy communication with the PC.

The capacitors have an extremely long life even at high temperature, and can be used at ambient temperatures of up to 60 °C.



Configuration with SITOP UPS500S:

24 V buffering for backing up process data and performing a controlled shutdown of a PC. To relieve the load on the UPS, the actuators are supplied directly from the power supply unit.

#### Design

#### SITOP UPS500S

- Compact 24 V/15 A basic units with integrated energy storage units of 2.5 or 5 kWs
- Digital inputs/outputs and USB interface
- For combination with up to three UPS501S expansion modules (5 kWs each) to extend the buffer time
- Metal housing in IP20 degree of protection for mounting on standard rails



SITOP UPS501S expansion module

- Additional energy storage (5 kWs)
- Up to 3 expansion modules can be connected to a SITOP UPS500S to extend the buffer times
- Can be easily connected to SITOP UPS500S via a user-friendly plug-in system
- · Complete with balancing and safety circuits

## SITOP DC UPS uninterruptible power supplies DC UPS with capacitors

#### DC UPS with capacitors

## Function

#### SITOP DC UPS software tool

Via the USB interface, all relevant messages about the status of the uninterruptible DC power supply can be transmitted to a PC (e.g. SIMATIC IPC). The DC UPS can also be configured via the USB interface.

The SITOP DC UPS software provides the user with a free tool that is extremely easy to use for the purpose of monitoring and configuring the DC UPS. Signals sent from the uninterruptible DC power supply can be processed on the PC. In monitoring mode, the statuses of the uninterruptible DC power supply are visualized on the PC.


Safe shutdown in the event of a power failure and automatic PC restart are supported. It is also possible to freely define responses to the different operating states of the uninterruptible DC power supply, so that extremely flexible integration into a wide variety of applications is possible.

Overview of configuration possibilities:

- Times for shutting down the PC
- UPS switch-off
- Further processing of all signals, e.g. linking to proprietary software or WinCC flexible
- Monitoring and display of UPS operating status
- OPC server for linking signals to proprietary applications
- · Automatic restarting of IPCs when power is restored during shutdown

The software runs under the operating systems Windows 2000, Windows XP, Windows Vista and Windows 7. Free download from:

http://support.automation.siemens.com/WW/view/en/48946053



Monitoring and configuration window of software V3 for SITOP DC UPS

## Technical specifications

The UPS500S can be extended to 20 kWs using UPS501S expansion modules (basic unit 5 kW + 3 expansion modules) to extend the buffer time.

The charging current can be set to 1 A or 2 A with the UPS500S.

Selection table SITOP UPS500 (optional with SITOP UPS501S expansion module) and mains buffering times

Buffering and charging times								
SITOP UPS500	S/501S configu	rations						
Basic unit	2.5 kWs	5 kWs	2.5 kWs	5 kWs	2.5 kWs	5 kWs	2.5 kWs	5 kWs
Expansion modules	-	-	$1 \times 5  \text{kWs}$	$1 \times 5  kWs$	$2 \times 5$ kWs	$2 \times 5  \text{kWs}$	$3 \times 5$ kWs	$3 \times 5$ kWs
Total energy	2.5 kWs	5 kWs	7.5 kWs	10 kWs	12.5 kWs	15 kWs	17.5 kWs	20 kWs
Load current	Buffer times							
0.5 A	134 s	236 s	390 s	478 s	632 s	748 s	851 s	1007 s
0.8 A	90 s	167 s	266 s	346 s	440 s	527 s	580 s	706 s
1 A	75 s	138 s	219 s	296 s	365 s	414 s	490 s	572 s
2 A	38 s	76 s	122 s	156 s	203 s	230 s	265 s	306 s
3 A	26 s	52 s	82 s	106 s	136 s	159 s	186 s	213 s
4 A	19 s	39 s	61 s	81 s	101 s	120 s	139 s	160 s
5 A	15 s	31 s	49 s	65 s	81 s	95 s	111 s	130 s
6 A	12 s	26 s	40 s	55 s	67 s	80 s	94 s	106 s
7 A	10 s	21 s	34 s	47 s	58 s	69 s	81 s	82 s
8 A	8 s	18 s	29 s	40 s	50 s	59 s	69 s	79 s
10 A	6 s	15 s	23 s	32 s	39 s	47 s	54 s	62 s
12 A	4 s	12 s	19 s	26 s	32 s	38 s	44 s	52 s
15 A	3 s	9 s	14 s	20 s	25 s	30 s	35 s	40 s
Charing curren	t Charging tim	es						
2 A	54 s	120 s	158 s	223 s	263 s	318 s	355 s	417 s
1 A	110 s	205 s	311 s	425 s	503 s	625 s	695 s	816 s

Important information for selecting the energy storage units:

When the mains buffering times were determined, the discharge period of new or non-aged, completely charged capacitors was used as a basis.

At a continuous ambient temperature of +50 °C, a loss of capacity of approx. 20% must be considered after a service life of 8 years.

DC UPS with capacitors

## DC UPS with capacitors

## Technical specifications

Article number	6EP1933-2EC41 <sup>1)</sup>	6EP1933-2EC51 <sup>1)</sup>
Product brand name	SITOP UPS500S	SITOP UPS500S
Type of current supply	Basic unit 2.5 kWs	Basic unit 5 kWs
Input	04.14	04)/
Supply voltage at DC Rated value	24 V	24 V
Voltage curve at input	DC	DC
input voltage range	22 29 V DC	22 29 V DC
Adjustable response value voltage for buffer connection preset		22.5 V
Adjustable response value voltage for buffer connection	22 25.5 V; Adjustable in 0.5 V increments	22 25.5 V; Adjustable in 0.5 V increments
Input current at rated input voltage 24 V Rated value	15.2 A; + approx. 2.3 A with empty energy storage (capacitor)	15.2 A; + approx. 2.3 A with empty energy storage (capacitor)
Mains buffering		
Type of energy storage	with capacitors	with capacitors
Design of the mains power cut bridging-connection	15 A for 3 s or 10 A for 6 s or 5 A for 15 s or 2 A for 38 s; longer buffering times with expansion modules	15 A for 9 s or 10 A for 15 s or 5 A for 31 s or 2 A for 76 s; longer buffering times with expansion modules
Energy content of energy storage	2.5 kW.s	5 kW.s
Charging current	1 A - 2 A	1 A - 2 A
adjustable charging current maximum Note	factory setting approx. 1 A	factory setting approx. 1 A
Output		
Output voltage		
<ul> <li>in normal operation at DC Rated value</li> </ul>	24 V	24 V
• in buffering mode at DC Rated value	24 V	24 V
ON-delay time typical	0.6 s	0.6 s
Voltage increase time of the output voltage typical	25 ms	25 ms
Output voltage in buffering mode at DC	24 24.7 V	24 24.7 V
Output current		
Rated value	15 A	15 A
<ul> <li>in normal operation</li> </ul>	0 15 A	0 15 A
<ul> <li>in buffering mode</li> </ul>	0 15 A	0 15 A
Peak current	25 A	25 A
Property of the output Short-circuit proof	Yes	Yes
Supplied active power typical	360 W	360 W
Efficiency		
Efficiency in percent		
<ul> <li>at rated output current for rated value of the output current typical</li> </ul>	97.5 %	97.5 %
Power loss [W]		
<ul> <li>at rated output current for rated value of the output current typical</li> </ul>	9 W	9 W
Protection and monitoring		
Product function		
<ul> <li>reverse polarity protection against energy storage unit polarity reversal</li> </ul>	Yes	Yes
<ul> <li>reverse polarity protection against input voltage polarity reversal</li> </ul>	Yes	Yes

# SITOP DC UPS uninterruptible power supplies DC UPS with capacitors

DC UPS with capacitors

Article number	6EP1933-2EC41 <sup>1)</sup>	6EP1933-2EC51 <sup>1)</sup>
Product brand name	SITOP UPS500S	SITOP UPS500S
Type of current supply	Basic unit 2.5 kWs	Basic unit 5 kWs
Signaling		
Display version		
<ul> <li>for normal operation</li> </ul>	Normal operation: LED green (OK), floating changeover contact "OK/Bat" to setting "OK" ("OK" means: Voltage of the supplying power supply unit is greater than cut-in threshold set at the DC UPS module); lack of buffer standby: LED red (ALARM), floating changeover contact "ALARM/BAT" to setting "ALARM"; energy storage > 85%: LED green (BAT > 85%), floating NO contact "BAT > 85" closed; permissible contact current capacity: DC 60 V/1 A or AC 30 V /1 A	Normal operation: LED green (OK), floating changeover contact "OK/Bat" to setting "OK" ("OK" means: Voltage o the supplying power supply unit is greater than cut-in threshold set at the DC UPS module); lack of buffer standby: LED red (ALARM), floating changeover contact "ALARM/BAT" to setting "ALARM"; energy storage > 859 LED green (BAT > 85%), floating NO contact "BAT > 85 closed; permissible contact current capacity: DC 60 V/ or AC 30 V /1 A
<ul> <li>in buffering mode</li> </ul>	Buffered mode: LED yellow (BAT), floating changeover contact "OK/BAT" to setting "BAT"; Prewarning buffer end after expiry of 80% of the available buffer time: LED red (ALARM), floating changeover contact "ALARM/BAT" to setting "ALARM"; Energy storage > 85%: LED green (BAT > 85%), floating NO contact "BAT > 85" closed	Buffered mode: LED yellow (BAT), floating changeover contact "OK/BAT" to setting "BAT"; Prewarning buffer en after expiry of 80% of the available buffer time: LED red (ALARM), floating changeover contact "ALARM/BAT" to setting "ALARM"; Energy storage > 85%: LED green (BAT > 85%), floating NO contact "BAT > 85" closed
Interface		
PC interface	Yes	Yes
Design of the interface	USB	USB
Safety		
Galvanic isolation between entrance and outlet	No	No
Operating resource protection class	Class III	Class III
Certificate of suitability		
CE marking	Yes	Yes
<ul> <li>as approval for USA</li> </ul>	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
<ul> <li>relating to ATEX</li> </ul>	-	-
C-Tick	Yes	Yes
Shipbuilding approval	ABS, DNV GL	ABS, DNV GL
Protection class IP	IP20	IP20
EMC		
Standard		
<ul> <li>for emitted interference</li> </ul>	EN 55022 Class B	EN 55022 Class B
<ul> <li>for interference immunity</li> </ul>	EN 61000-6-2	EN 61000-6-2
Operating data		
Environmental category acc. to IEC 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation

DC UPS with capacitors

## DC UPS with capacitors

## Technical specifications (continued)

Article number	6EP1933-2EC41 <sup>1)</sup>		6EP1933-2EC51 <sup>1)</sup>		
Product brand name	SITOP UPS500S		SITOP UPS500S		
Type of current supply	Basic unit 2.5 kWs		Basic unit 5 kWs		
Mechanics					
Type of electrical connection	screw-type terminals		screw-type terminal	S	
at input	24 V DC: 2 screw terminals for 1 4 r	nm²/17 11 AWG	24 V DC: 2 screw terminals for 1 4 mm <sup>2</sup> /17 11 AWG		
at output	24 V DC: 4 screw terminals for 1 4 r			rminals for 1 4 mm <sup>2</sup> /17 11 AWG	
<ul> <li>for battery module</li> </ul>	-		-		
<ul> <li>for control circuit and status message</li> </ul>	10 screw terminals for 0.5 2.5 mm²/20 13 AWG		- 10 screw terminals for 0.5 2.5 mm²/20 13 AWG		
Width of the enclosure	120 mm		120 mm		
Height of the enclosure	125 mm		125 mm		
Depth of the enclosure	125 mm		125 mm		
Required spacing	.20		120 11111		
• top	50 mm		50 mm		
• bottom	50 mm		50 mm		
• left	0 mm		0 mm		
	0 mm		0 mm		
right     Net weight	1 kg				
Product feature of the enclosure	i kg Yes		1 kg Yes		
housing for side-by-side mounting		1 F			
Mounting type	Snaps onto DIN rail EN 60715 35x7.5/	10		EN 60715 35x7.5/15	
Electrical accessories	Extension module SITOP UPS501S	Extension mode		110P 0P55015	
MTBF at 40 °C	638 570 h		459 137 h		
Reference code acc. to DIN EN 81346-2	Т	Т			
Other information	Specifications at rated input voltage a temperature +25 °C (unless otherwise			ed input voltage and ambient (unless otherwise specified)	
Article number	6EP1935-5PG01 <sup>1)</sup>	Article number		6EP1935-5PG01 <sup>1)</sup>	
Product brand name	SITOP UPS501	Product brand	name	SITOP UPS501	
Type of current supply	Extension module	Type of current	t supply	Extension module	
Input		Operating data	,		
•					
Voltage curve at input	DC	Ambient temper	rature		
<u> </u>	DC	Ambient temper • during operati		0 60 °C: with natural convection	
Voltage curve at input Mains buffering Type of energy storage		<ul> <li>during operati</li> </ul>	ion	0 60 °C; with natural convection -40 +70 °C	
Mains buffering Type of energy storage	DC with capacitors 5 kW.s	<ul><li> during operati</li><li> during transport</li></ul>	ion ort	0 60 °C; with natural convection -40 +70 °C -40 +70 °C	
Mains buffering Type of energy storage Energy content of energy storage Signaling	with capacitors	<ul> <li>during operati</li> <li>during transport</li> <li>during storage</li> <li>Environmental componential componential</li> </ul>	ion ort e	-40 +70 °C -40 +70 °C	
Mains buffering Type of energy storage Energy content of energy storage Signaling Display version	with capacitors	<ul> <li>during operati</li> <li>during transport</li> <li>during storage</li> <li>Environmental control</li> <li>IEC 60721</li> </ul>	ion ort e	-40 +70 °C -40 +70 °C	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation	with capacitors	during operati     during transpore     during storage     Environmental c     IEC 60721      Mechanics	ion ort e ategory acc. to	-40 +70 °C -40 +70 °C Climate class 3K3, no condensation	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface	with capacitors 5 kW.s -	during operati     during transpore     during storage     Environmental c     IEC 60721     Mechanics     Type of electricate	ion ort e ategory acc. to	-40 +70 °C -40 +70 °C Climate class 3K3, no condensation screw-type terminals	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface         Product component PC interface	with capacitors 5 kW.s -	during operati     during transpore     during storage     Environmental c     IEC 60721      Mechanics	ion ort e ategory acc. to	-40 +70 °C -40 +70 °C Climate class 3K3, no condensation screw-type terminals can be connected to SITOP	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface         Product component PC interface         Design of the interface	with capacitors 5 kW.s -	<ul> <li>during operati</li> <li>during transpo</li> <li>during storage</li> <li>Environmental of IEC 60721</li> <li>Mechanics</li> <li>Type of electrications</li> <li>at output</li> <li>for control circle</li> </ul>	ion prt ategory acc. to al connection	-40 +70 °C -40 +70 °C Climate class 3K3, no condensation screw-type terminals	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface         Product component PC interface         Design of the interface         Safety	with capacitors 5 kW.s -	<ul> <li>during operati</li> <li>during transpo</li> <li>during storage</li> <li>Environmental of IEC 60721</li> <li>Mechanics</li> <li>Type of electrication</li> <li>at output</li> <li>for control circon message</li> </ul>	ion ort e ategory acc. to al connection cuit and status	-40 +70 °C -40 +70 °C Climate class 3K3, no condensation screw-type terminals can be connected to SITOP UPS500S via a plug-in system -	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface         Product component PC interface         Design of the interface         Safety         Operating resource protection class	with capacitors 5 kW.s - No without	<ul> <li>during operati</li> <li>during transpo</li> <li>during storage</li> <li>Environmental of IEC 60721</li> <li>Mechanics</li> <li>Type of electrication</li> <li>at output</li> <li>for control circon message</li> <li>Width of the enditional</li> </ul>	ion ort e exategory acc. to al connection cuit and status closure	-40 +70 °C -40 +70 °C Climate class 3K3, no condensation screw-type terminals can be connected to SITOP UPS500S via a plug-in system - 70 mm	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface         Product component PC interface         Design of the interface         Safety         Operating resource protection class         Certificate of suitability	with capacitors 5 kW.s - No without Class III	<ul> <li>during operati</li> <li>during transpo</li> <li>during storage</li> <li>Environmental of IEC 60721</li> <li>Mechanics</li> <li>Type of electrication</li> <li>at output</li> <li>for control circon message</li> <li>Width of the endities</li> <li>Height of the endities</li> </ul>	ion port eategory acc. to al connection cuit and status closure iclosure	-40 +70 °C -40 +70 °C Climate class 3K3, no condensation screw-type terminals can be connected to SITOP UPS500S via a plug-in system - 70 mm 125 mm	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface         Product component PC interface         Design of the interface         Safety         Operating resource protection class         Certificate of suitability         • CE marking	with capacitors 5 kW.s - No without Class III Yes cULus-Listed (UL 508, CSA C22.2	<ul> <li>during operati</li> <li>during transport</li> <li>during storage</li> <li>Environmental of IEC 60721</li> <li>Mechanics</li> <li>Type of electrica</li> <li>at output</li> <li>for control circon message</li> <li>Width of the end</li> <li>Height of the end</li> <li>Depth of the end</li> <li>Required spacing</li> </ul>	ion prt eategory acc. to al connection cuit and status closure closure closure	-40 +70 °C -40 +70 °C Climate class 3K3, no condensation screw-type terminals can be connected to SITOP UPS500S via a plug-in system - 70 mm 125 mm 125 mm	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface         Product component PC interface         Design of the interface         Safety         Operating resource protection class         Certificate of suitability         • CE marking         • as approval for USA	with capacitors 5 kW.s - No without Class III Yes cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	<ul> <li>during operati</li> <li>during transpo</li> <li>during storage</li> <li>Environmental of IEC 60721</li> <li>Mechanics</li> <li>Type of electrica</li> <li>at output</li> <li>for control circo message</li> <li>Width of the end</li> <li>Height of the end</li> <li>Depth of the end</li> <li>Required spacin</li> <li>top</li> </ul>	ion prt eategory acc. to al connection cuit and status closure closure closure	-40 +70 °C -40 +70 °C Climate class 3K3, no condensation screw-type terminals can be connected to SITOP UPS500S via a plug-in system - 70 mm 125 mm 125 mm 50 mm	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface         Product component PC interface         Design of the interface         Safety         Operating resource protection class         Certificate of suitability         • CE marking         • as approval for USA	with capacitors 5 kW.s - No without Class III Yes cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 ATEX (EX) II 3G Ex nA IIC T4 Gc; cCSAus (CSA C22.2 No. 213,	<ul> <li>during operati</li> <li>during transpo</li> <li>during storage</li> <li>Environmental of IEC 60721</li> <li>Mechanics</li> <li>Type of electrica</li> <li>at output</li> <li>for control circo message</li> <li>Width of the eno Height of the eno Depth of the eno Required spacior</li> <li>top</li> <li>bottom</li> </ul>	ion prt eategory acc. to al connection cuit and status closure closure closure	-40 +70 °C -40 +70 °C Climate class 3K3, no condensation screw-type terminals can be connected to SITOP UPS500S via a plug-in system - 70 mm 125 mm 125 mm 50 mm 50 mm	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface         Product component PC interface         Design of the interface         Safety         Operating resource protection class         Certificate of suitability         • CE marking         • as approval for USA	with capacitors 5 kW.s - No without Class III Yes cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 ATEX (EX) II 3G Ex nA IIC T4 Gc; cCSAu (CSA C22.2 No. 213, ANSJ/ISA-12.12.01) Class I, Div. 2,	<ul> <li>during operati</li> <li>during transport</li> <li>during storage</li> <li>Environmental of IEC 60721</li> <li>Mechanics</li> <li>Type of electrication</li> <li>at output</li> <li>for control circonnessage</li> <li>Width of the endotes the endotes of th</li></ul>	ion prt eategory acc. to al connection cuit and status closure closure closure	-40 +70 °C -40 +70 °C Climate class 3K3, no condensation screw-type terminals can be connected to SITOP UPS500S via a plug-in system - 70 mm 125 mm 125 mm 50 mm 50 mm 0 mm	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface         Product component PC interface         Design of the interface         Safety         Operating resource protection class         Certificate of suitability         • CE marking         • as approval for USA         • relating to ATEX	with capacitors 5 kW.s - No without Class III Yes cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 ATEX (EX) II 3G Ex nA IIC T4 Gc; cCSAUS (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4	<ul> <li>during operati</li> <li>during transport</li> <li>during storage</li> <li>Environmental of IEC 60721</li> <li>Mechanics</li> <li>Type of electrication</li> <li>at output</li> <li>for control circonnessage</li> <li>Width of the endores</li> <li>Height of the endores</li> <li>Required spacing</li> <li>top</li> <li>bottom</li> <li>left</li> <li>right</li> </ul>	ion prt eategory acc. to al connection cuit and status closure closure closure	-40 +70 °C -40 +70 °C Climate class 3K3, no condensation screw-type terminals can be connected to SITOP UPS500S via a plug-in system - 70 mm 125 mm 125 mm 50 mm 50 mm 0 mm 0 mm	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface         Product component PC interface         Design of the interface         Safety         Operating resource protection class         Certificate of suitability         • CE marking         • as approval for USA         • relating to ATEX	with capacitors 5 kW.s - No without Class III Yes cUL us-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 ATEX (EX) II 3G Ex nA IIC T4 Gc; cCSAu (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4 Yes	<ul> <li>during operati</li> <li>during transport</li> <li>during storage</li> <li>Environmental of IEC 60721</li> <li>Mechanics</li> <li>Type of electrication</li> <li>at output</li> <li>for control circonnessage</li> <li>Width of the endores</li> <li>Height of the endores</li> <li>Required spacing</li> <li>top</li> <li>bottom</li> <li>left</li> <li>right</li> <li>Net weight</li> </ul>	ion prt eategory acc. to al connection cuit and status closure closure closure ng	<ul> <li>-40 +70 °C</li> <li>-40 +70 °C</li> <li>Climate class 3K3, no condensation</li> </ul> screw-type terminals <ul> <li>can be connected to SITOP</li> <li>UPS500S via a plug-in system</li> <li>-</li> <li>70 mm</li> <li>125 mm</li> <li>50 mm</li> <li>50 mm</li> <li>0 mm</li> <li>0 mm</li> <li>0 mm</li> <li>0 mm</li> <li>0.7 kg</li> </ul>	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface         Product component PC interface         Design of the interface         Safety         Operating resource protection class         Certificate of suitability         • CE marking         • as approval for USA         • relating to ATEX         • C-Tick         Shipbuilding approval	with capacitors 5 kW.s - No without Class III Yes cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 ATEX (EX) II 3G Ex nA IIC T4 GC; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4 Yes ABS, DNV GL	<ul> <li>during operati</li> <li>during transport</li> <li>during transport</li> <li>during storage</li> <li>Environmental of IEC 60721</li> <li>Mechanics</li> <li>Type of electrication</li> <li>at output</li> <li>for control circon message</li> <li>Width of the end</li> <li>Height of the end</li> <li>Height of the end</li> <li>Required spacing</li> <li>top</li> <li>bottom</li> <li>left</li> <li>right</li> <li>Net weight</li> <li>Product feature</li> </ul>	on ort e sategory acc. to al connection cuit and status closure closure closure ng	-40 +70 °C -40 +70 °C Climate class 3K3, no condensation screw-type terminals can be connected to SITOP UPS500S via a plug-in system - 70 mm 125 mm 125 mm 50 mm 50 mm 0 mm 0 mm	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface         Product component PC interface         Design of the interface         Safety         Operating resource protection class         Certificate of suitability         • CE marking         • as approval for USA         • relating to ATEX         • C-Tick         Shipbuilding approval	with capacitors 5 kW.s - No without Class III Yes cUL us-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 ATEX (EX) II 3G Ex nA IIC T4 Gc; cCSAu (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4 Yes	<ul> <li>during operati</li> <li>during transport</li> <li>during transport</li> <li>during storage</li> <li>Environmental of IEC 60721</li> <li>Mechanics</li> <li>Type of electrication</li> <li>at output</li> <li>for control circon message</li> <li>Width of the end</li> <li>Height of the end</li> <li>Height of the end</li> <li>Required spacing</li> <li>top</li> <li>bottom</li> <li>left</li> <li>right</li> <li>Net weight</li> <li>Product feature</li> </ul>	ion prt eategory acc. to al connection cuit and status closure closure closure ng	<ul> <li>-40 +70 °C</li> <li>-40 +70 °C</li> <li>Climate class 3K3, no condensation</li> <li>screw-type terminals</li> <li>can be connected to SITOP</li> <li>UPS500S via a plug-in system</li> <li>-</li> <li>70 mm</li> <li>125 mm</li> <li>50 mm</li> <li>50 mm</li> <li>50 mm</li> <li>0 mm</li> <li>0 mm</li> <li>0 mm</li> <li>0 mm</li> <li>0 rmm</li> <li>0 rm</li></ul>	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         nterface         Product component PC interface         Design of the interface         Safety         Operating resource protection class         Certificate of suitability         • CE marking         • as approval for USA         • relating to ATEX         • C-Tick         Shipbuilding approval	with capacitors 5 kW.s - No without Class III Yes cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 ATEX (EX) II 3G Ex nA IIC T4 GC; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4 Yes ABS, DNV GL	<ul> <li>during operati</li> <li>during transpo</li> <li>during storage</li> <li>Environmental of IEC 60721</li> <li>Mechanics</li> <li>Type of electrication</li> <li>at output</li> <li>for control circ message</li> <li>Width of the end</li> <li>Height of the end</li> <li>Height of the end</li> <li>Required spacint</li> <li>top</li> <li>bottom</li> <li>left</li> <li>right</li> <li>Net weight</li> <li>Product feature housing for side</li> <li>Mounting type</li> </ul>	on ort e sategory acc. to al connection cuit and status closure closure closure ng	<ul> <li>-40 +70 °C</li> <li>-40 +70 °C</li> <li>Climate class 3K3, no condensation</li> <li>screw-type terminals</li> <li>can be connected to SITOP</li> <li>UPS500S via a plug-in system</li> <li>-</li> <li>70 mm</li> <li>125 mm</li> <li>50 mm</li> <li>50 mm</li> <li>50 mm</li> <li>0 mm</li> <li>0 mm</li> <li>0 mm</li> <li>0 mm</li> <li>0 rmm</li> <li>0.7 kg</li> <li>Yes</li> <li>Snaps onto DIN rail EN 60715</li> <li>35x7.5/15</li> </ul>	
Mains buffering         Type of energy storage         Energy content of energy storage         Signaling         Display version         • for normal operation         Interface         Product component PC interface         Design of the interface         Safety         Operating resource protection class         Certificate of suitability         • CE marking	with capacitors 5 kW.s - No without Class III Yes cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 ATEX (EX) II 3G Ex nA IIC T4 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4 Yes ABS, DNV GL IP20	<ul> <li>during operati</li> <li>during transportion</li> <li>during storage</li> <li>Environmental of IEC 60721</li> <li>Mechanics</li> <li>Type of electrication</li> <li>at output</li> <li>for control circling</li> <li>for control circling</li> <li>message</li> <li>Width of the end</li> <li>Height of the end</li> <li>Height of the end</li> <li>Required spacint</li> <li>top</li> <li>bottom</li> <li>left</li> <li>right</li> <li>Net weight</li> <li>Product feature housing for side</li> </ul>	on ort eategory acc. to al connection cuit and status closure closure closure closure of the enclosure e-by-side mounting	<ul> <li>-40 +70 °C</li> <li>-40 +70 °C</li> <li>Climate class 3K3, no condensation</li> <li>screw-type terminals</li> <li>can be connected to SITOP</li> <li>UPS500S via a plug-in system</li> <li>-</li> <li>70 mm</li> <li>125 mm</li> <li>50 mm</li> <li>50 mm</li> <li>50 mm</li> <li>0 mm</li> <li>0 mm</li> <li>0 mm</li> <li>0 mm</li> <li>0 rmm</li> <li>0 rm</li></ul>	

## SITOP DC UPS uninterruptible power supplies DC UPS with capacitors

DC UPS with capacitors

Ordering data	Article No.	More information
SITOP UPS500S DC UPS basic device 15 A • With USB interface and 2.5 kWs • With USB interface and 5 kWs	6EP1933-2EC41 6EP1933-2EC51	The TIA Selection Tool offers detailed selection guidance according to criteria such as the required buffer time, load current or peak current: http://www.siemens.com/ts
SITOP UPS501S		
Expansion module 5 kWs for UPS500S	6EP1935-5PG01	
Accessories	Article No.	
Device identification label	3RT2900-1SB20	

DC UPS with battery modules

## Overview



By combining one DC UPS module SITOP UPS1600 with at least one UPS1100 battery module and a SITOP power supply unit, longer power failures can be bridged without any interruption. The intelligent battery management automatically detects the UPS1100 energy storage unit, ensures optimized temperaturespecific charging and continuous monitoring. The compact DC UPS modules have overload capability, for example, to supply the inrush current of industrial PCs. In stand-alone mode, they support starting from the battery.

The DC UPS communicates openly over a USB or Ethernet/ PROFINET port. It is easily integrated into the PC or PLC environment over the two Ethernet/PROFINET ports.

Total integration in TIA provides user-friendly engineering in the TIA Portal and is supported with ready-to-use function blocks for S7 user programs and WinCC faceplates for fast visualization.

SITOP Manager also enables simple monitoring and configuration in PC systems, e.g. shutting down multiple PCs according to the master-slave principle.

The UPS1600 modules with Ethernet/PROFINET ports have an OPC UA server, with which the DC UPS can communicate with both PCs and PLCs, even from different manufacturers, thanks to the open communication standard. Parameter assignment and the diagnostics of the uninterruptible power supply is possible via the open interface.

The integrated web server supports remote monitoring of the DC UPS.

## Benefits

- 24 V buffering for a few hours for the purpose of continuing processes
- Open communication over USB or two Ethernet/PROFINET ports
- High-performance DC UPS modules in space-saving, slim design
- High overload capability for mains and buffering operation
- Starting from the battery module supports stand-alone mode, e.g. for starting generators
- Easy configuration thanks to automatic detection of battery modules
- High reliability and availability due to monitoring of the operational readiness, battery feeder, aging and charging status
- Battery protecting charging due to temperature-specific charging characteristic
- Defined shutdown of several PCs or controllers on one UPS (versions with Ethernet/PROFINET)
- Remote monitoring via integrated web server (versions with Ethernet/PROFINET)
- Time-saving engineering in PC-based systems via SITOP Manager (versions with USB or Ethernet/PROFINET)
- Integrated OPC UA server facilitates flexible, multi-vendor communication with other systems (versions with Ethernet/ PROFINET)
- Full integration in TIA saves time and costs during the planning stage and in operation (versions with Ethernet/ PROFINET)
- User-friendly engineering in the TIA Portal
- SIMATIC S7 function blocks for easy integration in STEP 7 user programs
- Fast integration in operator control and monitoring with WinCC faceplates
- Direct integration in SIMATIC PCS 7 via SITOP library

## SITOP DC UPS uninterruptible power supplies DC UPS with battery modules

SITOP UPS1600 DC UPS modules


#### Application

The battery modules that can be connected in parallel bridge power failures for a few hours. This supports the continued operation of processes or parts of them. The function "Starting from the battery" means that the UPS1600 can also be used in stand-alone mode without connection to the supply.

Depending on the communication requirements between the DC UPS and the automation components to be protected against power failure, the version of UPS1600 can be selected accordingly.


#### Buffering of simple automation applications

In simple applications with mini PLCs (e.g. obstruction lights, stand-alone hydro-electric plants), 24 V buffering is performed by the UPS1600 without a communications interface. The status messages are transferred to the PLC via the digital outputs (isolated).



#### Buffering of applications with automation computer


The UPS1600 with a USB interface is used to buffer automation solutions that are controlled by an industrial PC. All operating and configuring data is communicated over the PC interface.



Communication over Ethernet/PROFINET offers the most comprehensive possibilities for diagnostics and system integration. The UPS1600 can be directly integrated into the LAN infrastructure over its two ports.


## Buffering of applications with networked (Industrial Ethernet) automation computers

The UPS1600 with Industrial Ethernet interface protects complex PC-based applications from power failure. Configuration and monitoring is performed with the SITOP Manager PC software. It also supports defined shutdown of several PCs in accordance with the master-slave principle.



## Buffering of applications with networked (PROFINET) automation components

For buffering sensitive plant components (e.g. a pumping station with telecontrol) or complete controller solutions (e.g. machine tools) that are integrated into a networked automation solution, the UPS1600 with PROFINET is the perfect choice. Total integration in TIA offers unique advantages for engineering and operation (e.g. diagnostics or visualization). For example, in buffer mode, several controllers can be brought to a defined independently of each other.



DC UPS with battery modules

## SITOP UPS1600 DC UPS modules

## Design



- Compact DC UPS modules UPS1600 24 V/10 A, 20A and 40 A with digital inputs and outputs, optionally with USB interface or two Ethernet/PROFINET ports
- UPS1100 battery modules 1.2 Ah, 3.2 Ah, 7 Ah and 12 Ah with lead rechargeable batteries for use in high temperatures, UPS1100 2.5 Ah battery module with pure-lead rechargeable batteries and UPS1100 5 Ah battery module with lithium-ion technology.

#### Function

#### Web server

The SITOP UPS1600 with Ethernet/PROFINET has an integrated web server that supports remote monitoring and control of the uninterruptible power supply in 5 languages

(DE / EN / FR / IT / ES). Using HTTPS ensures encrypted and safe data transmission.

Remote monitoring and control of:


- Hardware configuration data
- Remote monitoring
- Operating data of the UPS1600 basic unit and the connected UPS1100 battery module
- Alarm messages

Remote access via:

- Microsoft Internet Explorer >V8, Mozilla Firefox >V40, and Google Chrome >V44
- IP address
- Password

#### SIEMENS

DC UPS MONITOR



The password-protected web server offers a view of the configuration and operating data.

## Function (continued)

#### Software

Software tools support convenient integration of the SITOP UPS1600 in both PC-based and PLC-based systems. They make configuring and visualizing the DC UPS easier and the user benefits from the high performance of the SITOP UPS1600.

#### Software for open, PC-based automation systems

SITOP Manager—the tool for commissioning, engineering and monitoring of communication-capable SITOP power supplies

SITOP Manager is the medium for all users who do not work with SIMATIC STEP 7 in the TIA Portal or with SIMATIC PCS 7. It manages all communication-capable power supplies in a communication network and enables their commissioning, online and offline engineering, diagnostics as well as operator control and monitoring. With the help of the SITOP Shutdown Service (autonomous function of the SITOP Manager), for example, it also supports continuous monitoring and specific shutdown of one or more PCs in case of a power failure. Connection of the SITOP UPS1600 uninterruptible power supply with the USB interface is implemented with the SITOP Gateway Service (autonomous function of the SITOP Manager). Data transmission is secure thanks to encrypted communication.

SITOP Manager is available as a free download in SIOS. It supports the following SITOP devices:

- Requirement for using SITOP Manager V1.0 with SITOP UPS1600 PN/USB
- SITOP UPS1600 10 A, 20 A as of product state (PS) "6", firmware V2.2.2 and higher
- SITOP UPS1600 40 A as of product state (PS) "3", firmware V2.2.2 and higher

SITOP Manager is the innovative alternative to the current UPS Manager (today's configuration tool of the SITOP UPS1600) and will replace it in the long term.


#### Functions of the SITOP Manager

- Integrated engineering, monitoring, diagnostics and service functions save time and operating costs
- Usability via the web interface simplifies automation projects
- Stability and quality prevent plant failures
- Shutting down specific PCs prevents data loss in the event of a power failure
- Possibility to configure multiple SITOP UPS1600 PN/USBs via a single SITOP Manager project file reduces overhead and time, thus saving costs
- The option to make configuration changes during operation (CiR) reduces plant downtimes
- The firmware update option ensures that the SITOP UPS1600 is always up-to-date.
- Since SITOP Manager supports Microsoft Windows, it can be used on all common PCs
- Built-in versatility since the SITOP Manager can be operated on a wide variety of end devices, such as PCs/industrial PCs, tablets and mobiles
- Secure, encrypted communication according to the Siemens security concepts ('Security-in-depth' model)

DC UPS with battery modules

SITOP UPS1600 DC UPS modules

## Function (continued)



SITOP Manager UPS1600 offline, including saving of offline project to a project file

SIEMENS			SITOP Manager
Lopped in arc admin Lopout			F English 🔳
OFFLINE Project • my-poul000 • my-shutdown-service	0×8 0×	Gisprentice     General     General     General	Shutdown Sanda (V1.0.0
• my-ups1600 © AM	6×	Ceneral coordinated by \$100 Manager (secondended)	
ONLINE Connections	-	# via STOP Manager	
psu     PsuB000 4 x 104 (V1.4.0)     BUFB600 100ms/H04 (V1.4.0) [V]     shutdean service		Anigred bothe composed pro	
* shutdown service Shutdown Service (V1.0.0)	*		
pro		coordinated by PSUBSODUPS1600	
@ And		Anigree Buffer semprenet [192,166.0.3 DPC Uk per [460 Ukr name animatic semprenet ] Paraget ]	

#### SITOP Manager PSU8600 Engineering SDS online

Free download at:

https://support.industry.siemens.com/cs/ww/en/view/109760607

#### Software for TIA-based automation systems


For convenient integration of the DC UPS in the TIA environment, different software modules are available.

Engineering is simple via the TIA Portal. The data for UPS1600 is stored in the hardware catalog version V14 and higher. Special function blocks for SIMATIC S7-300, S7-400, S7-1200 and S7-1500 also support integration in the STEP 7 user program.

The comprehensive diagnostics data of the UPS1600 power supply can be visualized using prepared WinCC faceplates.

#### **TIA Portal**

- Convenient and fail-safe integration of SITOP UPS1600 in the PROFINET network by means of drag-and-drop
- Convenient configuration of SITOP UPS1600 basic units with Ethernet/PROFINET and the UPS1100 battery module simply by selecting from the TIA Portal hardware catalog
- Free HSP (hardware support packages) available for the TIA Portal:
- http://support.automation.siemens.com/WW/view/en/72341852
  Free GSD file (generic station description) for STEP 7 V5.5:
- http://support.automation.siemens.com/WW/view/en/75854605



Establishing the PROFINET connection between the SITOP UPS1600 and the controller is easy and fail-safe in the TIA Portal

#### STEP 7 function blocks

Function blocks are available for STEP 7 user programs on SIMATIC S7-300/400/1200/1500. They allow further processing of the DC UPS operating data.

- Function blocks for STEP 7 V5.5
- Function blocks for STEP 7 in the TIA Portal

#### Free download at:

http://support.automation.siemens.com/WW/view/en/78817848

## Faceplates for WinCC

Ready-to-use faceplates save programming time for visualization of the uninterruptible power supply. The faceplates show all relevant statuses and values of the DC UPS. They are available for the following systems:

- Faceplates for WinCC from Version V7.4
- Faceplates for WinCC flexible 2008 SP3
- Faceplates for WinCC Comfort/Advanced/Professional in the TIA Portal from version V14

#### Free download at:

http://support.automation.siemens.com/WW/view/en/78817848



The pre-compiled WinCC faceplates show all the relevant UPS data in a clearly comprehensible display. An icon with color coding for the operating state is also available

DC UPS with battery modules

#### SITOP UPS1600 DC UPS modules

#### Function (continued)

#### Software for SIMATIC PCS 7 process control system

The SITOP library is available with blocks and faceplates for direct integration into SIMATIC PCS 7. The SW blocks in the SIMATIC S7 supply the faceplate on the user interface of the process control system with operating and diagnostics data, generate messages and ensure connection to the maintenance system of PCS 7.

This means that PCS 7 users automatically receive information about operating state conditions, maintenance requirements (e.g. battery replacement) and disturbances (e.g. power failures). This ensures constant transparency of the 24V supply in the control system. The SITOP library is supported in SIMATIC PCS 7 with SP2 as from version V8.0.

Free download at: https://support.industry.siemens.com/cs/ww/en/view/109476154

#### Technical specifications

The table shows the maximum buffering times for the SITOP UPS1100 battery modules for different load currents:

The SITOP Selection Tool offers detailed product selection guidance according to criteria such as the required backup time, load current, peak current and battery connection threshold:

http://www.siemens.com/tst

Product brand name	SITOP UPS1100	SITOP UPS1100	SITOP UPS1100	SITOP UPS1100	SITOP UPS1100	SITOP UPS1100
Type of power supply	24 V/1.2 Ah	24 V/2.5 Ah high temperature	24 V/3.2 Ah	24 V/5 Ah LiFePo	24 V/7 Ah	24 V/12 Ah
Article No.	6EP4131-0GB00-0AY0	6EP4132-GB00-0AY0	6EP4133-0GB00-0AY0	6EP4133-0JB00-0AY0	6EP4134-0GB00-0AY0	6EP4135-0GB00-0AY0
Load current	Buffering times *					
1 A	27 min	1 h 30 min	2 h	4 h	5 h	8 h 30 min
2 A	14 min	50 min	1 h	2 h 10 min	2 h 40 min	4 h 80 min
3 A	10 min	36 min	45 min	1 h 30 min	1 h 50 min	3 h 10 min
4 A	7 min 50 s	26 min	34 min	1 h 10 min	1 h 20 min	2 h 30 min
6 A	4 min 40 s	15 min	21 min	48 min	48 min	1 h 30 min
8 A	3 min	11 min	15 min	37 min	34 min	1 h
10 A	1 min 30 s	6 min 40 s	9 min 30 s	26 min	21 min	42 min
12 A	-	5 min 40 s	8 min 10 s	23 min	19 min	37 min
14 A	-	4 min 40 s	6 min 50 s	21 min	16 min	32 min
16 A	-	3 min 40 s	5 min 30 s	18 min	13 min	27 min
20 A	-	1 min 40 s	2 min 50 s	13 min	7 min 50 s	17 min
30 A	-	-	-	-	3 min 50 s	10 min
40 A	-	-	-	-	1 min 40 s	5 min 30 s
Ambient temperature	Service life (with drop	p to approx. 80% of or	iginal capacity), depen	ding on battery tempe	rature, approx.	
+20 °C	4 years	10 years	4 years	15 years	4 years	4 years
+30 °C	2 years	7 years	2 years	10 years	2 years	2 years

+30 °C 2 vears / vears +40 °C 1 year 3 years 1 year 9 years 1 year 1 year +50 °C 0.5 years 1.5 years 0.5 years 2 years 0.5 years 0.5 years +60 °C 1 year

\* The determination of the buffer times is based on the discharge period of new and completely charged battery modules with a battery temperature of not less than +25 °C until shutdown of the DC UPS (19 volt). Buffer times for additional values can be determined using the SITOP Selection Tool: www.siemens.com/tst.

Important information for selecting the battery capacity:

Determination of the mains buffering time is based on the discharge period of a new and completely charged battery module at a battery temperature not below +25 °C.

According to the Eurobat definition, battery aging reduces the available battery capacity to typically around 80% of the original capacity value (1.2 Ah/3.2 Ah/7 Ah, etc.) and increases the internal resistance. When the message "Battery charge > 85%" appears, only around 80% x 85% = approx. 68% of the originally available capacity can be assumed at the end of the battery service life.

At battery temperatures below +25 °C, the available capacity drops approx. by another 30%, at +5 °C battery temperature, to around 70% of the roughly remaining 68%. Only about 48% of the original capacity is then available.

A significantly larger battery capacity must therefore be selected when configuring the plant: A drop to approx. 50% is compensated for by selecting 1 / approx. 0.5 = doubling the required battery capacity (required as per the table for the relevant load current and the relevant buffering time). A remaining approx. 68% capacity is compensated for by selecting 1 / approx. 0.68 = approx. 1.5 times the battery capacity. A remaining approx. 48% capacity is compensated for by selecting 1 / approx. 0.48 = approx. 2.1 times the battery capacity.

## SITOP DC UPS uninterruptible power supplies DC UPS with battery modules

SITOP UPS1600 DC UPS modules

## Technical specifications (continued)

#### Recommendation:

Instead of installing additional battery capacity, regular battery replacement halfway through the expected service life (reduction of capacity to approx. 80% in accordance to the Eurobat definition) can be more advisable for the following reasons: capacity does not drop below 100% until the halfway point of the expected battery life (or slightly beyond). With regular replacement after this point, only the single battery capacity (instead of double capacity) must be installed due to aging (-> neutral in price with regard to battery module costs, and only requires half the space). The UPS1600 monitors battery aging with a regular resistor load test (R-test) and signals a recommendation for battery replacement (LED 2: BAT FAULT in red).

Replacing the battery after half its service life dispenses with the large variance in the residual capacity at the end of the service life, which is not well defined defined by battery manufacturers (after the defined lifespan, a percentage of batteries are above and also below the average 80% residual capacity, so even if double the capacity is installed, the influence of aging at the end of service life is not reliably compensated for, rather only on average). When replacing the battery after half of the expected service life, the configured buffering time is maintained with considerably greater reliability.

In the case of batteries stored in cool conditions (not above +25 °C) and for not longer than approximately 4 months, the following service life can be assumed, strongly dependent on battery temperature: In normal cases (installation in the coolest location in the control cabinet at approx. +30 °C), the battery should be replaced with single installed battery capacity in accordance with the selection table after 1 year of operation.

#### Technical specifications

Article number	6EP4134-3AB00-0AY0 <sup>1)</sup> 6EP4134-3AB00-1AY0 <sup>1)</sup> 6EP4134-3AB00-2AY0 <sup>1)</sup>	6EP4136-3AB00-0AY0 <sup>1)</sup> 6EP4136-3AB00-1AY0 <sup>1)</sup> 6EP4136-3AB00-2AY0 <sup>1)</sup>	6EP4137-3AB00-0AY0 <sup>1)</sup> 6EP4137-3AB00-1AY0 <sup>1)</sup> 6EP4137-3AB00-2AY0 <sup>1)</sup>	
Product brand name	SITOP UPS1600	SITOP UPS1600	SITOP UPS1600	
Type of current supply	DC UPS 24 V/10 A	DC UPS 24 V/20 A	DC UPS 24 V/40 A	
Input				
Supply voltage at DC Rated value	24 V	24 V	24 V	
Voltage curve at input	DC	DC	DC	
input voltage range	21 29 V DC	21 29 V DC	21 29 V DC	
Adjustable response value voltage for buffer connection preset	21.5 V	21.5 V	21.5 V	
Adjustable response value voltage for buffer connection	21 25 V; Adjustable: 21 V, 21.5 V, 22 V, 22.5 V, 23 V, 24 V, 25 V DC	21 25 V; Adjustable: 21 V, 21.5 V, 22 V, 22.5 V, 23 V, 24 V, 25 V DC	21 25 V; Adjustable: 21 V, 21.5 V, 22 V, 22.5 V, 23 V, 24 V, 25 V DC	
Input current at rated input voltage 24 V Rated value	14 A; for max. charging current (3 A)	25 A; for max. charging current (4 A)	46 A; for max. charging current (5 A)	
Mains buffering				
Type of energy storage	with batteries	with batteries	with batteries	
Design of the mains power cut bridging-connection	Adjustable range using rotary coding switch: 0.5 min, 1 min, 2 min, 5 min, 10 min, 20 min, max. buffering time	Adjustable range using rotary coding switch: 0.5 min, 1 min, 2 min, 5 min, 10 min, 20 min, max. buffering time	Adjustable range using rotary coding switch: 0.5 min, 1 min, 2 min, 5 min, 10 min, 20 min, max. buffering time	
Charging current	0.1 A - 3 A	0.1 A - 4 A	0.1 A - 5 A	
adjustable charging current maximum Note	Automatically depending on battery module	Automatically depending on battery module	Automatically depending on battery module	
Output				
Output voltage				
<ul> <li>in normal operation at DC Rated value</li> </ul>	24 V	24 V	24 V	
• in buffering mode at DC Rated value	24 V	24 V	24 V	
Formula for output voltage	V <sub>in</sub> - approx. 0.2 V	V <sub>in</sub> - approx. 0.2 V	V <sub>in</sub> - approx. 0.2 V	
ON-delay time typical	<1s	<1s	<1s	
Voltage increase time of the output voltage typical	60 ms	60 ms	60 ms	
Output voltage in buffering mode at DC	18.5 27 V	18.5 27 V	18.5 27 V	
Output current				
Rated value	10 A	20 A	40 A	
<ul> <li>in normal operation</li> </ul>	0 30 A	0 60 A	0 120 A	
<ul> <li>in buffering mode</li> </ul>	0 30 A	0 60 A	0 120 A	
Peak current	30 A	60 A	120 A	
Property of the output Short-circuit proof	Yes	Yes	Yes	

DC UPS with battery modules

## SITOP UPS1600 DC UPS modules

Technical specifications (cont	inued)		
Article number	6EP4134-3AB00-0AY0 <sup>1)</sup> 6EP4134-3AB00-1AY0 <sup>1)</sup> 6EP4134-3AB00-2AY0 <sup>1)</sup>	6EP4136-3AB00-0AY0 <sup>1)</sup> 6EP4136-3AB00-1AY0 <sup>1)</sup> 6EP4136-3AB00-2AY0 <sup>1)</sup>	6EP4137-3AB00-0AY0 <sup>1)</sup> 6EP4137-3AB00-1AY0 <sup>1)</sup> 6EP4137-3AB00-2AY0 <sup>1)</sup>
Product brand name	SITOP UPS1600	SITOP UPS1600	SITOP UPS1600
Type of current supply	DC UPS 24 V/10 A	DC UPS 24 V/20 A	DC UPS 24 V/40 A
Output (continued)			
Design of short-circuit protection	Limitation to 3 x I rated for 30 ms/min; through-conductivity for 1.5 x I rated for 5 sec/min	Limitation to 3 x I rated for 30 ms/min; through-conductivity for 1.5 x I rated for 5 sec/min	Limitation to 3 x I rated for 30 ms/min; through-conductivity for 1.5 x I rated for 5 sec/min
Supplied active power typical	240 W	480 W	960 W
Efficiency			
Efficiency in percent <ul> <li>at rated output current for rated</li> </ul>	97.5 %	97.7 %	98.5 %
<ul> <li>value of the output current typical</li> <li>in case of accumulator operation</li> </ul>	97.5 %	97.7 %	98.5 %
typical Power loss [W]	91.5 %	31.1 /0	90.0 %
<ul> <li>at rated output current for rated value of the output current typical</li> </ul>	6 W	10 W	15 W
<ul> <li>in case of accumulator operation typical</li> </ul>	6 W	10 W	15 W
Protection and monitoring			
Product function			
<ul> <li>reverse polarity protection against energy storage unit polarity reversal</li> </ul>	Yes	Yes	Yes
<ul> <li>reverse polarity protection against input voltage polarity reversal</li> </ul>	Yes	Yes	Yes
Signaling			
Display version			
<ul> <li>for normal operation</li> <li>in buffering mode</li> </ul>	the supplying power supply unit is greater than cut-in threshold set at the DC UPS module); Lack of buffer standby: LED red (alarm), floating changeover contact "Alarm/Bat" to setting "Alarm"; Battery replacement required: LED red (alarm) flashing with approx. 0.25 Hz; floating changeover contact "Alarm/Bat" switching with approx. 0.25 Hz; Energy storage > 85%: LED green (Bat > 85%), floating NO contact "Bat > 85%), floating NO contact "Bat > 85%), floating NO contact current capacity: DC 60 V/1 A or AC 30 V /1 A Buffered mode: LED yellow (Bat), floating changeover contact "OK/Bat" to setting "Bat"; Prewarning battery voltage < 20.4 VDC: LED red (alarm), floating changeover contact "Alarm/ Bat" to setting "Alarm"; Energy storage > 85%: LED green (Bat > 85%),	Normal operation: LED green (OK), floating changeover contact "Bat/OK" to setting "OK" ("OK" means: Voltage of the supplying power supply unit is greater than cut-in threshold set at the DC UPS module); Lack of buffer standby: LED red (alarm), floating changeover contact "Alarm/Bat" to setting "Alarm"; Battery replacement required: LED red (alarm) floating with approx. 0.25 Hz; floating changeover contact "Alarm/Bat" switching with approx. 0.25 Hz; floating changeover contact "Alarm/Bat" switching with approx. 0.25 Hz; Energy storage > 85%: LED green (Bat > 85%), floating NO contact "Bat > 85" closed; Permissible contact current capacity: DC 60 V/1 A or AC 30 V /1 A Buffered mode: LED yellow (Bat), floating changeover contact "OK/Bat" to setting "Bat"; Prewarning battery voltage < 20.4 VDC: LED red (alarm), floating changeover contact "Alarm/ Bat" to setting "Alarm"; Energy storage > 85%: LED green (Bat > 85%),	Normal operation: LED green (OK), floating changeover contact "Bat/OK" to setting "OK" ("OK" means: Voltage of the supplying power supply unit is greater than cut-in threshold set at the DC UPS module); Lack of buffer standby: LED red (alarm), floating changeover contact "Alarm/Bat" to setting "Alarm"; Battery replacement required: LED red (alarm) flashing with approx. 0.25 Hz; floating changeover contact "Alarm/Bat" switching with approx. 0.25 Hz; Energy storage > 85%: LED green (Bat > 85%), floating NO contact "Bat > 85" closed; Permissible contact current capacity: DC 60 V/1 A or AC 30 V/1 A Buffered mode: LED yellow (Bat), floating changeover contact "OK/Bat" to setting "Bat"; Prewarning battery voltage < 20.4 VDC: LED red (alarm), floating changeover contact "Alarm/ Bat" to setting "Alarm"; Energy storage > 85%: LED green (Bat > 85%),
Interface	floating NO contact "Bat > 85" closed	floating NO contact "Bat > 85" closed	floating NO contact "Bat > 85" closed
	No	No	No
PC interface	No	No	No
Design of the interface	without	without	without
Safety	No	No	No
Galvanic isolation between entrance and outlet	No Class III	No Closs III	No Class III
Operating resource protection class Certificate of suitability		Class III	Class III
CE marking	Yes	Yes	Yes
<ul><li> as approval for USA</li><li> relating to ATEX</li></ul>		cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cULus Class I, Div. 2 (ANSI/ISA-12.12.01-2015, CSA C22.2 No. 213-15) Group ABCD, T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2,	CULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cULus Class I, Div. 2 (ANSI/ISA-12.12.01-2015, CSA C22.2 No. 213-15) Group ABCD, T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2,
• C-Tick	Group ABCD, T4	Group ABCD, T4	Group ABCD, T4

Yes

Yes

8

Yes

# SITOP DC UPS uninterruptible power supplies DC UPS with battery modules

## SITOP UPS1600 DC UPS modules

Article number	6EP4134-3AB00-0AY0 <sup>1)</sup> 6EP4134-3AB00-1AY0 <sup>1)</sup> 6EP4134-3AB00-2AY0 <sup>1)</sup>	6EP4136-3AB00-0AY0 <sup>1)</sup> 6EP4136-3AB00-1AY0 <sup>1)</sup> 6EP4136-3AB00-2AY0 <sup>1)</sup>	6EP4137-3AB00-0AY0 <sup>1)</sup> 6EP4137-3AB00-1AY0 <sup>1)</sup> 6EP4137-3AB00-2AY0 <sup>1)</sup>
Product brand name	SITOP UPS1600	SITOP UPS1600	SITOP UPS1600
Type of current supply	DC UPS 24 V/10 A	DC UPS 24 V/20 A	DC UPS 24 V/40 A
Safety (continued)			
Type of certification CB-certificate	Yes	Yes	Yes
Shipbuilding approval	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL
Protection class IP	IP20	IP20	IP20
EMC			
Standard			
<ul> <li>for emitted interference</li> </ul>	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
<ul> <li>for interference immunity</li> </ul>	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data			
Ambient temperature			
during operation	-25 +70 °C; with natural convection	-25 +70 °C; with natural convection	-25 +70 °C; with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C
Environmental category acc. to IEC 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics			
Type of electrical connection	screw-type terminals	screw-type terminals	screw-type terminals
• at input	24 V DC: 2 screw terminals for 0.2 6 mm <sup>2</sup> /24 13 AWG	24 V DC: 2 screw terminals for 0.2 6 mm <sup>2</sup> /24 13 AWG	24 V DC: 2 screw terminals for 0.5 16 mm <sup>2</sup> /20 6 AWG
at output	24 V DC: 2 screw terminals for 0.2 6 mm <sup>2</sup> /24 13 AWG	24 V DC: 2 screw terminals for 0.2 6 mm <sup>2</sup> /24 13 AWG	24 V DC: 2 screw terminals for 0.5 16 mm²/20 6 AWG
<ul> <li>for battery module</li> </ul>	24 V DC: 2 screw terminals for 0.2 6 mm <sup>2</sup> /24 13 AWG	24 V DC: 2 screw terminals for 0.2 6 mm <sup>2</sup> /24 13 AWG	24 V DC: 2 screw terminals for 0.5 16 mm <sup>2</sup> /20 6 AWG
<ul> <li>for control circuit and status message</li> </ul>	14 screw terminals for 0.2 1.5 mm <sup>2</sup> /24 16 AWG	14 screw terminals for 0.2 1.5 mm <sup>2</sup> /24 16 AWG	14 screw terminals for 0.2 1.5 mm <sup>2</sup> /24 16 AWG
Width of the enclosure	50 mm	50 mm	70 mm
Height of the enclosure	139 mm	139 mm	139 mm
Depth of the enclosure	125 mm	125 mm	150 mm
Required spacing			
• top	50 mm	50 mm	50 mm
bottom	50 mm	50 mm	50 mm
• left	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm
Net weight	0.38 kg	0.39 kg	0.65 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes
Mounting type	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
Electrical accessories	Battery module	Battery module	Battery module
MTBF at 40 °C	415 574 h	408 654 h	372 738 h
Reference code acc. to	Т	Т	Т

<sup>1)</sup> Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Ordering data	Article No.	Accessories	Article No.
SITOP UPS1600 24 V/10 A • With USB interface • With PROFINET/Ethernet: two RJ45 sockets (2 port switch)	6EP4134-3AB00-0AY0 6EP4134-3AB00-1AY0 6EP4134-3AB00-2AY0	Device identification label	3RT2900-1SB20
SITOP UPS1600, 24 V/20 A • With USB interface • With PROFINET/Ethernet: two RJ45 sockets (2 port switch)	6EP4136-3AB00-0AY0 6EP4136-3AB00-1AY0 6EP4136-3AB00-2AY0		
SITOP UPS1600 24 V/40 A • With USB interface • With PROFINET/Ethernet: two RJ45 sockets (2 port switch)	6EP4137-3AB00-0AY0 6EP4137-3AB00-1AY0 6EP4137-3AB00-2AY0		

DC UPS with battery modules

## Overview



Maintenance-free SITOP UPS1100 battery modules with 1.2 Ah up to 12 Ah and various types of energy storage (lead, pure lead, lithium iron phosphate = LiFePo) for SITOP UPS1600 DC UPS modules. The intelligent UPS1600 battery management charges the UPS1100 with the optimal temperature-controlled charging characteristics and monitors the status (operating data and diagnostics information) of the connected battery modules via the energy storage link. For longer buffer times, up to six battery modules can be connected in parallel. These can be mounted onto a standard mounting rail or directly to the wall.

## Technical specifications

Article number	6EP4131-0GB00- 0AY0 <sup>1)</sup>	6EP4132-0GB00- 0AY0 <sup>1)</sup>	6EP4133-0GB00- 0AY0 <sup>1)</sup>	6EP4133-0JB00- 0AY0 <sup>1)</sup>	6EP4134-0GB00- 0AY0 <sup>1)</sup>	6EP4135-0GB00- 0AY0 <sup>1)</sup>
Product	SITOP UPS1100					
Product type	Battery module 1.2 Ah	Battery module 2.5 Ah	Battery module 3.2 Ah	Battery module 5 Ah	Battery module 7 Ah	Battery module 12 Ah
Charging current charging voltage						
End-of-charge voltage at DC						
<ul> <li>at -10 °C recommended</li> </ul>	28 V	28 V	28 V	28.8 V	28 V	28 V
<ul> <li>at 0 °C recommended</li> </ul>	28 V	28 V	28 V	28.8 V	28 V	28 V
<ul> <li>at 10 °C recommended</li> </ul>	27.8 V	27.8 V	27.8 V	28.8 V	27.8 V	27.8 V
<ul> <li>at 20 °C recommended</li> </ul>	27.3 V	27.3 V	27.3 V	28.8 V	27.3 V	27.3 V
<ul> <li>at 30 °C recommended</li> </ul>	26.8 V	26.8 V	26.8 V	28.8 V	26.8 V	26.8 V
<ul> <li>at 40 °C recommended</li> </ul>	26.6 V	26.6 V	26.6 V	28.8 V	26.6 V	26.6 V
<ul> <li>at 50 °C recommended</li> </ul>	26.3 V	26.3 V	26.3 V	28.8 V	26.3 V	26.3 V
<ul> <li>at 60 °C recommended</li> </ul>	-	26 V	-	-	-	-
Output						
Rated current value	10 A	20 A	20 A	20 A	40 A	40 A
Iout rated						
Permissible charging current, max.	0.3 A	5 A	0.8 A	2.1 A	1.75 A	3 A
Rated voltage V <sub>out</sub> DC	24 V					

# SITOP DC UPS uninterruptible power supplies DC UPS with battery modules

SITOP UPS1100 battery modules

Article number	6EP4131-0GB00- 0AY0 <sup>1)</sup>	6EP4132-0GB00- 0AY0 <sup>1)</sup>	6EP4133-0GB00- 0AY0 <sup>1)</sup>	6EP4133-0JB00- 0AY0 <sup>1)</sup>	6EP4134-0GB00- 0AY0 <sup>1)</sup>	6EP4135-0GB00- 0AY0 <sup>1)</sup>
Product	SITOP UPS1100	SITOP UPS1100	SITOP UPS1100	SITOP UPS1100	SITOP UPS1100	SITOP UPS1100
Product type	Battery module	Battery module	Battery module	Battery module	Battery module	Battery module
0-4-4-	1.2 Ah	2.5 Ah	3.2 Ah	5 Ah	7 Ah	12 Ah
Safety Short-circuit	Battery fuse	Battery fuse	Battery fuse	Battery fuse	Battery fuse	Battery fuse
protection		25 A/32 V (solid-state circuitry blade-type fuse + support)	25 A/32 V (solid-state circuitry blade-type fuse + support)		2x 25 A/32 V (solid- state circuitry blade- type fuse + support)	2x 25 A/32 V (soli state circuitry blac type fuse + suppo
Design of the overload protection	Valve control	Valve control	Valve control	Valve control	Valve control	Valve control
Status display	LED green: Battery OK; LED flashing green: Error or warning; OFF: No communication	LED green: Battery OK; LED flashing green: Error or warning; OFF: No communication	LED green: Battery OK; LED flashing green: Error or warning; OFF: No communication	LED green: Battery OK; LED flashing green: Error or warning; OFF: No communication	LED green: Battery OK; LED flashing green: Error or warning; OFF: No communication	LED green: Batter OK; LED flashing green: Error or warning; OFF: No communication
Safety						
Protection class	Class III	Class III	Class III	Class III	Class III	Class III
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20	IP20	IP20
Approvals						
CE mark	Yes	Yes	Yes	Yes	Yes	Yes
UL/cUL (CSA) approval	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627	cURus-Recognize (UL 1778, CSA C2 No. 107.1), File E219627
Explosion protection <sup>2)</sup>	IECEX EX NA NC IIC T4 Gc; cCSAus (CSA C22.2 No. 213- M1987, ANSI/ISA- 12.12.01-2013) Class I, Div. 2, Group ABCD, T4	IECEX EX NA NC IIC T4 Gc; cCSAus (CSA C22.2 No. 213- M1987, ANSI/ISA- 12.12.01-2013) Class I, Div. 2, Group ABCD, T4	IECEX EX NA NC IIC T4 Gc; cCSAus (CSA C22.2 No. 213- M1987, ANSI/ISA- 12.12.01-2013) Class I, Div. 2, Group ABCD, T4	-	IECEx Ex nA nC IIC T4 Gc; cCSAus (CSA C22.2 No. 213- M1987, ANSI/ISA- 12.12.01-2013) Class I, Div. 2, Group ABCD, T4	IECEx Ex nA nC I T4 Gc; cCSAus (CSA C22.2 No. 2 M1987, ANSI/ISA 12.12.01-2013) Class I, Div. 2, Group ABCD, T4
Approvals	Yes	Yes	Yes	Yes	Yes	Yes
Marine approval	DNV GL, ABS	DNV GL, ABS	DNV GL, ABS	DNV GL, ABS	DNV GL, ABS	DNV GL, ABS
environmental conditions						
Operating data note	For storage, mounting and operation of lead- acid batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/ EN 50272-2) must be observed. You must ensure that the battery site is suffi- ciently ventilated. Possible sources of ignition must be at least 50 cm away.	For storage, mounting and operation of lead- acid batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/ EN 50272-2) must be observed. You must ensure that the battery site is suffi- ciently ventilated. Possible sources of ignition must be at least 50 cm away.	For storage, mounting and operation of lead- acid batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/ EN 50272-2) must be observed. You must ensure that the battery site is suffi- ciently ventilated. Possible sources of ignition must be at least 50 cm away.	For storage, mounting and operation of batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/ EN 50272-2) must be observed.	relevant DIN/VDE regulations or country-specific regulations (e.g.	For storage, mounting and operation of lead- acid batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/ EN 50272-2) must observed. You mu ensure that the battery site is suff ciently venilated. Possible sources ignition must be a least 50 cm away.
Ambient temperature						
<ul> <li>during operation</li> </ul>	-15 +50 °C	-40 +60 °C	-15 +50 °C	-20 +50 °C	-15 +50 °C	-15 +50 °C
during transport	-20 +50 °C	-40 +60 °C	-20 +50 °C	-40 +60 °C	-20 +50 °C	-20 +50 °C
during storage	-20 +50 °C	-40 +60 °C	-20 +50 °C	-40 +60 °C	-20 +50 °C	-20 +50 °C
Relative temporary capacity loss at 20 °C in a month typical	3 %	3 %	3 %	3 %	3 %	3 %

in a month typical

DC UPS with battery modules

## SITOP UPS1100 battery modules

## Technical specifications (continued)

Article number	6EP4131-0GB00- 0AY0 <sup>1)</sup>	6EP4132-0GB00- 0AY0 <sup>1)</sup>	6EP4133-0GB00- 0AY0 <sup>1)</sup>	6EP4133-0JB00- 0AY0 <sup>1)</sup>	6EP4134-0GB00- 0AY0 <sup>1)</sup>	6EP4135-0GB00- 0AY0 <sup>1)</sup>
Product	SITOP UPS1100	SITOP UPS1100	SITOP UPS1100	SITOP UPS1100	SITOP UPS1100	SITOP UPS1100
Product type	Battery module 1.2 Ah	Battery module 2.5 Ah	Battery module 3.2 Ah	Battery module 5 Ah	Battery module 7 Ah	Battery module 12 Ah
Service life						
Service life of energy storage						
<ul> <li>typical Note</li> </ul>	capacity falls to 80 % of original capacity	capacity falls to 80 % of original capacity	capacity falls to 80 % of original capacity	capacity falls to 80 % of original capacity	capacity falls to 80 % of original capacity	capacity falls to 80 % of original capacity
<ul> <li>at 20 °C typical</li> </ul>	4 y	10 y	4 y	15 y	4 y	4 y
<ul> <li>at 30 °C typical</li> </ul>	2 у	7у	2 у	10 y	2 у	2 у
<ul> <li>at 40 °C typical</li> </ul>	1 y	3 у	1 y	9 у	1 y	1 y
<ul> <li>at 50 °C typical</li> </ul>	0.5 y	1.5 y	0.5 y	2 у	0.5 y	0.5 y
<ul> <li>at 60 °C typical</li> </ul>	-	1 y	-	-	-	-
Ambient temperature during storage Note	storage and operating temperature, other factors such as the duration of the storage period and the charge status during storage have a decisive influence on the possible useful life. Batteries should therefore be stored as briefly as possible,	life. Batteries should therefore be stored as briefly as possible,	life. Batteries should therefore be stored as briefly as possible,	Along with the storage and operating temperature, other factors such as the duration of the storage period and the charge status during storage have a decisive influence on the possible useful life. Batteries should therefore be stored as briefly as possible, always fully charged, and within the temperature range 0 to +20 °C.	life. Batteries should therefore be stored as briefly as possible,	life. Batteries should therefore be stored
Mechanics						
Connection technology	screw-type terminals	screw-type terminals	screw-type terminals	screw-type terminals	screw-type terminals	screw-type terminals
Connection for power supply unit		1 screw terminal each for 0.2 $\dots$ 6 mm <sup>2</sup> for + BAT and - BAT	1 screw terminal each for 0.2 $\dots$ 6 mm <sup>2</sup> for + BAT and - BAT	1 screw terminal each for 0.5 $\dots$ 16 mm <sup>2</sup> for + BAT and - BAT	1 screw terminal each for 0.5 16 mm <sup>2</sup> for + BAT and - BAT	1 screw terminal each for 0.5 16 mm for + BAT and - BAT
Type of electrical connection for control circuit and status message	1 screw terminal each for 0.14 4 mm <sup>2</sup>	1 screw terminal each for 0.14 4 mm <sup>2</sup>	1 screw terminal each for 0.14 4 mm <sup>2</sup>	1 screw terminal each for 0.14 4 mm <sup>2</sup>	1 screw terminal each for 0.14 4 mm <sup>2</sup>	1 screw terminal each for 0.14 4 mm <sup>2</sup>
Product component belonging to	Accessories pack with solid-state circuitry fuse 15 A	Accessories pack with solid-state circuitry fuse 25 A	Accessories pack with solid-state circuitry fuse 25 A	Accessories pack with solid-state circuitry fuse 25 A	Accessories pack with solid-state circuitry fuse 25 A	Accessories pack with solid-state circuitry fuse 25 A
Width of the enclosure	89 mm	265 mm	190 mm	189 mm	186 mm	253 mm
Height of the enclosure	130 mm	115 mm	170 mm	186 mm	186 mm	186 mm
Depth of the enclosure	107 mm	76 mm	78.7 mm	113 mm	110 mm	110 mm
Installation width	89 mm	265 mm	190 mm	189 mm	186 mm	253 mm
Installation height	145 mm	130 mm	184 mm	201 mm	201 mm	201 mm
Weight, approx.	1.9 kg	3.7 kg	3.8 kg	3.4 kg	6.1 kg	9.8 kg
Installation	snaps onto DIN rail EN 60715 35x7.5/15 or keyhole mounting for hooking in to M4 screws	snaps onto DIN rail EN 60715 35x7.5/15 or keyhole mounting for hooking in to M4 screws	snaps onto DIN rail EN 60715 35x15 or keyhole mounting for hooking in to M4 screws	snaps onto DIN rail EN 60715 35x15 or keyhole mounting for hooking in to M4 screws	can be screwed onto flat surface (keyhole	
Number of cells	12	12	12	16	12	12
Battery	1.2 A·h	2.5 A·h	3.2 A·h	5 A·h	7 A·h	12 A·h
Reference code acc. to DIN EN 81346-2	G	G	G	G	G	G
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified) ambient temperature +2	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

1) Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

<sup>2)</sup> Explosion protection guidelines can prohibit the parallel circuit for battery modules. Please observe the related standard..

# SITOP DC UPS uninterruptible power supplies DC UPS with battery modules

SITOP UPS1100 battery modules

			circi of office battery modul
Ordering data	Article No.	Accessories	Article No.
SITOP UPS1100 battery module 1.2 Ah	6EP4131-0GB00-0AY0	Device identification label	3RT2900-1SB20
With maintenance-free, sealed rechargeable lead-acid batteries for DC UPS module SITOP UPS1600, 10 A			
SITOP UPS1100 battery module 3.2 Ah	6EP4133-0GB00-0AY0		
With maintenance-free, sealed rechargeable lead-acid batteries for DC UPS module SITOP UPS1600, 10 A and 20 A			
SITOP UPS1100 battery module 5 Ah, LiFePo	6EP4133-0JB00-0AY0		
With maintenance-free, sealed rechargeable lithium iron phosphate batteries for DC UPS module SITOP UPS1600, 10 A and 20 A			
SITOP UPS1100 battery module 7 Ah	6EP4134-0GB00-0AY0		
With maintenance-free, sealed rechargeable lead-acid batteries for DC UPS module SITOP UPS1600, 10 A, 20 A and 40 A			
SITOP UPS1100 battery module 12 Ah	6EP4135-0GB00-0AY0		
With maintenance-free, sealed rechargeable lead-acid batteries for DC UPS module SITOP UPS1600, 10A, 20A and 40A			
SITOP UPS1100 battery module 2.5 Ah, high temperature	6EP4132-0GB00-0AY0		
With maintenance-free, closed lead-acid batteries for DC UPS module SITOP UPS1600, 10 A and 20 A			

DC UPS with battery modules

## SITOP DC UPS

## Overview



By combining a DC UPS module with at least one 24 V battery module and a SITOP power supply unit, longer power failures can be bridged without any interruption. Even if a greater buffering current is required, the DC UPS with maintenance-free lead battery provides optimum safety. It spans power failures up to several hours long and delivers up to 40 A.


#### Benefits

- 24 V buffering for a few hours for the purpose of continuing processes
- Maintenance-free battery modules from 1.2 to 12 Ah
- High reliability and availability due to monitoring of the operational readiness, battery feeder, aging and charging status
- Long operating life of loads and batteries due to integrated battery management
- Settings by means of DIP switches: Battery connection threshold, end-of-charge voltage, charging current, bridging time
- SW tool, free of charge, for easy configuring and integrating in PC-based systems

#### Application

These battery modules that can be connected in parallel bridge power failures for a few hours. This enables processes or parts of them to be continued, measured values to be recorded without interruption and communication to be maintained. Highperformance industrial PCs that have to be shut down also have somewhat higher energy demands. Especially if a large panel continues to be operated during the shutdown. The DC UPS is used, for example, in machine tool production, in the textile industry, in all types of production lines, bottling plants or also for the obstacle lights of wind power plants.

The serial or USB interface and a free software tool enable easy communication with a PC.



Configuration with SITOP DC UPS and battery module: 24 V buffering to maintain communication, signaling and sensor measured values. To relieve the load on the UPS, the actuators are supplied directly from the power supply unit.

#### Design

- DC UPS modules 24 V/6 A, 15 A, 40 A
- · Digital inputs/outputs, optionally with serial or USB interface



- Battery modules 1.2 Ah, 3.2 Ah, 7 Ah, 12 Ah with lead rechargeable batteries of corrosion-resistant lead-calcium high-performance grid plates and glass fiber
- Battery module 2.5 Ah with "high-temperature battery" of pure lead



DC UPS with battery modules

SITOP DC UPS

## Function

## SITOP DC UPS software tool

Via the USB interface, all relevant messages about the status of the uninterruptible DC power supply can be transmitted to a PC (e.g. SIMATIC IPC). The DC UPS can also be configured via the USB interface.

The SITOP DC UPS software provides the user with a free tool that is extremely easy to use for the purpose of monitoring and configuring the DC UPS. Signals sent from the uninterruptible DC power supply can be processed on the PC. In monitoring mode, the statuses of the uninterruptible DC power supply are visualized on the PC.


Safe shutdown in the event of a power failure and automatic PC restart are supported. It is also possible to freely define responses to the different operating states of the uninterruptible DC power supply, so that extremely flexible integration into a wide variety of applications is possible.

Overview of configuration possibilities:

- Times for shutting down the PC
- UPS switch-off
- Further processing of all signals, e.g. linking to proprietary software or WinCC flexible
- Monitoring and display of UPS operating status
- OPC server for linking signals to proprietary applications
- Automatic restarting of IPCs when power is restored during shutdown

The software runs under the operating systems Windows 2000, Windows XP, Windows Vista and Windows 7. Free download from:

http://support.automation.siemens.com/WW/view/en/48946053



Monitoring and configuration window of software V3 for SITOP DC UPS  $% \left( \mathcal{A}^{\prime}\right) =\left( \mathcal{A}^{\prime}\right) \left( \mathcal{A}^{\prime}\right)$ 

DC UPS with battery modules

#### SITOP DC UPS

#### Technical specifications

The table shows the maximum buffering times for the battery modules for different load currents.

The TIA Selection Tool offers detailed product selection guidance according to criteria such as the required buffer time, load current, peak current and battery connection threshold: http://www.siemens.com/tst

Load current	Battery module 1.2 Ah (6EP1935-6MC01)	Battery module 3.2 Ah (6EP1935-6MD11)	Battery module 7 Ah (6EP1935-6ME21)	Battery module 12 Ah (6EP1935-6MF01)	Battery module 2.5 Ah (6EP1935-6MD31)
1 A	34.5 min	2.6 h	5.4 h	9 h	2 h
2 A	15 min	1 h	2.6 h	4.6 h	1 h
3 A	9 min	39.3 min	1.6 h	2.9 h	37.5 min
4 A	6.5 min	27.1 min	1.2 h	2.2 h	27 min
6 A	3.5 min	17.5 min	41 min	1.2 h	17.6 min
8 A	2 min	12.1 min	28.6 min	53.3 min	12.5 min
10 A	1 min	9 min	21.8 min	43.5 min	8.8 min
12 A	-	7 min	17.3 min	33.3 min	6.8 min
14 A	-	5 min	15.1 min	27.5 min	5.1 min
16 A	-	4 min	12.5 min	23.8 min	4.3 min
20 A	-	1 min	9.1 min	20.1 min	-
25 A	-	-	-	12.6 min	-
30 A	-	-	-	9.1 min	-
35 A	-	-	-	17.1 min. (2 x 12 Ah)	-
40 A	-	-	-	13.5 min. (2 x 12 Ah)	-

Important information for selecting the battery capacity:

Determination of the mains buffering times is based on the discharge period of new or non-aged, completely charged battery modules at a battery temperature not below +25 °C to the shutdown of the DC UPS.

Battery aging reduces the still available battery capacity up until the end of the service life to typically around 80% of the original capacity value when new (1.2 Ah/3.2 Ah/7 Ah, etc.) and the internal resistance increases. When the message "Battery charge > 85%" appears, only around 80% x 85% = approx. 68% of the originally available capacity can be assumed at the end of the battery service life.

At battery temperatures below +25 °C, the available capacity drops approx. by another 30% at +5 °C battery temperature, to around 70% of the roughly remaining 68%. Only about 48% of the original capacity is then available.

A significantly larger battery capacity must therefore be selected when configuring the plant: A drop to approx. 50% is compensated for by selecting 1 / approx. 0.5 = around double the battery capacity (required as per the table for the relevant load current and the relevant buffering time). A remaining approx. 0.68 = approx. 1.5 times the battery capacity. A remaining approx. 48% capacity is compensated for by selecting 1 / approx. 0.48 = approx. 2.1 times the battery capacity.

#### Recommendation:

Instead of installing additional battery capacity, regular battery replacement halfway through the expected service life (reduction of capacity to approx. 80% according to the Eurobat definition) can be more advisable for the following reasons: Capacity does not drop below 100% until the halfway point of the expected battery life (or slightly beyond). With regular replacement after this point, only the single battery capacity (instead of double capacity) must be installed due to aging (-> neutral in price with regard to battery module costs, and only requires half the space). The UPS1600 monitors battery aging with a regular resistor load test (R test) and signals a recommendation for battery replacement (LED 2: BAT FAULT in orange). Replacing the battery after half its service life dispenses above all with the large scatter range of the residual capacity at the end of the service life, which is not accurately defined by battery manufacturers (after the full time, many batteries are above, but many are also below the average 80% residual capacity, so even if double the capacity is installed, the influence of aging at the end of service life is not reliably compensated for, rather only typically) -> When replacing after half the expected service life, the configured buffering time is maintained with considerably greater reliability.

In the case of batteries stored in cool conditions (not above +25 °C) and for not longer than approximately 4 months, the following service life can be assumed, strongly dependent on battery temperature:

Battery temperature	Drop to approx. 50% of residual capacity	Recommendation: Replace (at 100% of residual capacity) all	
+20 °C	4 years	2 years	
+30 °C	2 years	1 year	
+40 °C	1 year	0.5 years	Install double capacity and replace 1 x per year

In normal cases (installation in the coolest location in the control cabinet at approx. +30 °C), the battery should be replaced with single installed battery capacity in accordance with the selection table after 1 year of operation!

- On the DC UPS module 40 A, at least 2 battery modules of 7 Ah or higher must be connected in parallel for output currents > 30 A. When connecting battery modules in parallel, you must ensure identical capacity and aging.
- After a power failure, the battery module is disconnected from the loads at the end of the selected buffering time either automatically or electronically by opening the On/Off control circuit, and as soon as the 24 V input voltage is available again, it is quickly re-charged with the charging current of the relevant DC UPS module (with I-U charge characteristic: First constant current I for fast charging, and changeover to constant voltage U to maintain the charge when the battery is almost full).

# SITOP DC UPS uninterruptible power supplies DC UPS with battery modules

SITOP DC UPS

# Technical specifications

Article number	6EP1931-2DC21 <sup>1)</sup> 6EP1931-2DC31 <sup>1)</sup> 6EP1931-2DC42 <sup>1)</sup>	6EP1931-2EC21 <sup>1)</sup> 6EP1931-2EC31 <sup>1)</sup> 6EP1931-2EC42 <sup>1)</sup>	6EP1931-2FC21 <sup>1)</sup> 6EP1931-2FC42 <sup>1)</sup>
Product brand name	SITOP DC UPS module	SITOP DC UPS module	SITOP DC UPS module
Type of current supply	DC UPS 24 V/6 A	DC UPS 24 V/15 A	DC UPS 24 V/40 A
Input			
Supply voltage at DC Rated value	24 V	24 V	24 V
Voltage curve at input	DC	DC	DC
input voltage range	22 29 V DC	22 29 V DC	22 29 V DC
Adjustable response value voltage for buffer connection preset	22.5 V	22.5 V	22.5 V
Adjustable response value voltage for buffer connection	22 25.5 V; Adjustable in 0.5 V increments	22 25.5 V; Adjustable in 0.5 V increments	22 25.5 V; Adjustable in 0.5 V increments
Input current at rated input voltage 24 V Rated value	6 A; + approx. 0.6 A with empty battery	15 A; + approx. 1 A with empty battery	40 A; + approx. 2.6 A with empty battery
Mains buffering			
Type of energy storage	with batteries	with batteries	with batteries
Design of the mains power cut bridging-connection	Dependent on connected battery and load current, see selection table battery module and mains buffering times as well as the relevant important information notes!	Dependent on connected battery and load current, see selection table battery module and mains buffering times as well as the relevant important information notes!	Dependent on connected battery and load current, see selection table battery module and mains buffering times as well as the relevant important information notes!
Charging current	0.2 A - 0.4 A	0.35 A - 0.7 A	1 A - 2 A
adjustable charging current maximum Note	factory setting approx. 0.4 A	factory setting approx. 0.7 A	factory setting approx. 2 A
Output			
Output voltage			
<ul> <li>in normal operation at DC Rated value</li> </ul>	24 V	24 V	24 V
• in buffering mode at DC Rated value		24 V	24 V
Formula for output voltage	V <sub>in</sub> - approx. 0.5 V	V <sub>in</sub> - approx. 0.5 V	V <sub>in</sub> - approx. 0.5 V
ON-delay time typical	1 s	1s	1s
Voltage increase time of the output voltage typical	60 ms	60 ms	360 ms
Output voltage in buffering mode at DC	19 28.5 V	19 28.5 V	19 28.5 V
Output current		45.4	40.4
Rated value	6 A	15 A	40 A
• in normal operation	0 6 A	0 15 A	0 40 A
• in buffering mode	0 6 A	0 15 A	0 40 A
Peak current Property of the output Short-circuit proof	6.3 A Yes	15.7 A Yes	42 A
Supplied active power typical	144 W	360 W	960 W
Efficiency	1 T T V V		500 W
Efficiency in percent			
at rated output current for rated value of the output current typical	95 %	96.2 %	97.2 %
<ul> <li>in case of accumulator operation typical</li> </ul>	94.5 %	96 %	96.9 %
Power loss [W]			
• at rated output current for rated value of the output current typical	7 W	14 W	28.6 W
<ul> <li>in case of accumulator operation typical</li> </ul>	8 W	15 W	33.6 W
Protection and monitoring Product function			
<ul> <li>reverse polarity protection against energy storage unit polarity reversal</li> </ul>	Yes	Yes	Yes
<ul> <li>reverse polarity protection against input voltage polarity reversal</li> </ul>	Yes	Yes	Yes

# SITOP DC UPS uninterruptible power supplies

DC UPS with battery modules

# SITOP DC UPS

### Technical specifications (continued)

recinical specifications (cont	,		
Article number	6EP1931-2DC21 <sup>1)</sup> 6EP1931-2DC31 <sup>1)</sup> 6EP1931-2DC42 <sup>1)</sup>	6EP1931-2EC21 <sup>1)</sup> 6EP1931-2EC31 <sup>1)</sup> 6EP1931-2EC42 <sup>1)</sup>	6EP1931-2FC21 <sup>1)</sup> 6EP1931-2FC42 <sup>1)</sup>
Product brand name	SITOP DC UPS module	SITOP DC UPS module	SITOP DC UPS module
Type of current supply	DC UPS 24 V/6 A	DC UPS 24 V/15 A	DC UPS 24 V/40 A
Signaling			
Display version			
• for normal operation	the supplying power supply unit is greater than cut-in threshold set at the DC UPS module); Lack of buffer standby: LED red (alarm), floating changeover contact "Alarm/Bat" to setting "Alarm"; Battery replacement required: LED red (alarm) flashing with approx. 0.25 Hz; floating changeover contact "Alarm/Bat" switching with approx. 0.25 Hz; Energy storage > 85%: LED green (Bat > 85%), floating NO contact "Bat > 85" closed; Permissible contact current capacity: DC 60 V/1 A or AC 30 V /1 A	the supplying power supply unit is greater than cut-in threshold set at the DC UPS module); Lack of buffer standby: LED red (alarm), floating changeover contact "Alarm/Bat" to setting "Alarm"; Battery replacement required: LED red (alarm) flashing with approx. 0.25 Hz, floating changeover contact "Alarm/Bat" switching with approx. 0.25 Hz; Energy storage > 85%: LED green (Bat > 85%), floating NO contact "Bat > 85" closed; Permissible contact current capacity: DC 60 V/1 A or AC 30 V /1 A	Normal operation: LED green (OK), floating changeover contact "Bat/OK" to setting "OK" ("OK" means: Voltage of the supplying power supply unit is greater than cut-in threshold set at the DC UPS module); Lack of buffer standby: LED red (alarm), floating changeover contact "Alarm/Bat" to setting "Alarm"; Battery replacement required: LED red (alarm) flashing with approx. 0.25 Hz; floating changeover contact "Alarm/Bat" switching with approx. 0.25 Hz; Energy storage > 85%; LED green (Bat > 85%), floating NO contact "Bat > 85" closed; Permissible contact current capacity: DC 60 V/1 A or AC 30 V /1 A
in buffering mode	Buffered mode: LED yellow (Bat), floating changeover contact "OK/Bat" to setting "Bat"; Prewarning battery voltage < 20.4 VDC: LED red (alarm), floating changeover contact "Alarm/ Bat" to setting "Alarm"; Energy storage > 85%: LED green (Bat > 85%), floating NO contact "Bat > 85" closed	Buffered mode: LED yellow (Bat), floating changeover contact "OK/Bat" to setting "Bat"; Prewarning battery voltage < 20.4 VDC: LED red (alarm), floating changeover contact "Alarm/ Bat" to setting "Alarm"; Energy storage > 85%: LED green (Bat > 85%), floating NO contact "Bat > 85" closed	Buffered mode: LED yellow (Bat), floating changeover contact "OK/Bat" to setting "Bat"; Prewarning battery voltage < 20.4 VDC: LED red (alarm), floating changeover contact "Alarm/ Bat" to setting "Alarm"; Energy storage > 85%: LED green (Bat > 85%), floating NO contact "Bat > 85" closed
Interface			
Product component PC interface	No	No	No
Design of the interface	without	without	without
Safety			
Galvanic isolation between entrance and outlet	No	No	No
Operating resource protection class	Class III	Class III	Class III
Certificate of suitability			
<ul> <li>CE marking</li> </ul>	Yes	Yes	Yes
<ul> <li>as approval for USA</li> </ul>	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
<ul> <li>relating to ATEX</li> </ul>	-	-	-
C-Tick	No	No	No
Shipbuilding approval	ABS, DNV GL	ABS, DNV GL	ABS, DNV GL
Protection class IP	IP20	IP20	IP20
EMC			
Standard			
<ul> <li>for emitted interference</li> </ul>	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
<ul> <li>for interference immunity</li> </ul>	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data			
Ambient temperature			
during operation	-25 +60 °C: with natural convection	-25 +60 °C; with natural convection	-25 +60 °C; with natural convection
during transport	-40 +85 °C	-40 +85 °C	-40 +85 °C
during storage	-40 +85 °C	-40 +85 °C	-40 +85 °C
Environmental category acc. to	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation
IEC 60721			

# SITOP DC UPS uninterruptible power supplies DC UPS with battery modules

SITOP DC UPS

Article number	6EP1931-2DC21 <sup>1)</sup> 6EP1931-2DC31 <sup>1)</sup> 6EP1931-2DC42 <sup>1)</sup>	6EP1931-2EC21 <sup>1)</sup> 6EP1931-2EC31 <sup>1)</sup> 6EP1931-2EC42 <sup>1)</sup>	6EP1931-2FC21 <sup>1)</sup> 6EP1931-2FC42 <sup>1)</sup>
Product brand name	SITOP DC UPS module	SITOP DC UPS module	SITOP DC UPS module
Type of current supply	DC UPS 24 V/6 A	DC UPS 24 V/15 A	DC UPS 24 V/40 A
Mechanics			
Type of electrical connection	screw-type terminals	screw-type terminals	screw-type terminals
at input	24 V DC: 2 screw terminals for 1 4 mm <sup>2</sup> /17 11 AWG	24 V DC: 2 screw terminals for 1 4 mm <sup>2</sup> /17 11 AWG	24 V DC: 2 screw terminals for 0.33 10 mm <sup>2</sup> /22 7 AWG
at output	24 V DC: 4 screw terminals for 1 4 mm <sup>2</sup> /17 11 AWG	24 V DC: 4 screw terminals for 1 4 mm <sup>2</sup> /17 11 AWG	24 V DC: 2 screw terminals for 0.33 10 mm <sup>2</sup> /22 7 AWG
<ul> <li>for battery module</li> </ul>	24 V DC: 2 screw terminals for 1 4 mm <sup>2</sup> /17 11 AWG	24 V DC: 2 screw terminals for 1 4 mm <sup>2</sup> /17 11 AWG	24 V DC: 2 screw terminals for 0.33 10 mm <sup>2</sup> /22 7 AWG
<ul> <li>for control circuit and status message</li> </ul>	10 screw terminals for 0.5 2.5 mm <sup>2</sup> /20 13 AWG	10 screw terminals for 0.5 2.5 mm <sup>2</sup> /20 13 AWG	10 screw terminals for 0.5 2.5 mm <sup>2</sup> /20 13 AWG
Width of the enclosure	50 mm	50 mm	102 mm
Height of the enclosure	125 mm	125 mm	125 mm
Depth of the enclosure	125 mm	125 mm	125 mm
Required spacing			
• top	50 mm	50 mm	50 mm
• bottom	50 mm	50 mm	50 mm
• left	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm
Net weight	0.4 kg	0.4 kg	1.1 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes
Mounting type	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
Electrical accessories	Battery module	Battery module	Battery module
MTBF at 40 °C	1 085 776 h	791 139 h	522 739 h
Reference code acc. to DIN EN 81346-2	т	Т	т
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input vol and ambient temperature +25 ° (unless otherwise specified)

<sup>1)</sup> Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Ordering data	Article No.
DC UPS module 6 A	6EP1931-2DC21
• with serial interface	6EP1931-2DC31
• with USB interface	6EP1931-2DC42
DC UPS module 15 A	6EP1931-2EC21
• with serial interface	6EP1931-2EC31
• with USB interface	6EP1931-2EC42
<b>DC UPS module 40 A</b>	6EP1931-2FC21
• with USB interface	6EP1931-2FC42

# 8

# SITOP DC UPS uninterruptible power supplies

DC UPS with battery modules

**DC UPS battery modules** 

### Overview



Maintenance-free battery modules with 1.2 Ah up to 12 Ah (lead-gel accumulator) for ambient temperatures from -15 to +40 °C as well as high-temperature battery module with 2.5 Ah (pure-lead accumulator) for ambient temperatures of -40 °C to +60 °C. The battery modules are completely prewired with battery retainer and terminals. For longer buffer times, the battery modules can be connected in parallel. Mounting onto standard mounting rail or directly to the wall.

### Technical specifications

Article number	6EP1935-6MC01	6EP1935-6MD31	6EP1935-6MD11	6EP1935-6ME21	6EP1935-6MF01
Product	•	SITOP Battery module	•	•	•
Product type	Battery module 1.2 Ah	Battery module 2.5 Ah	Battery module 3.2 Ah	Battery module 7 Ah	Battery module 12 Ah
Charging current charging voltage					
End-of-charge voltage at DC					
<ul> <li>at -10 °C recommended</li> </ul>	29 V	29 V	29 V	29 V	29 V
<ul> <li>at 0 °C recommended</li> </ul>	28.4 V	28.6 V	28.4 V	28.4 V	28.4 V
<ul> <li>at 10 °C recommended</li> </ul>	27.8 V	28.3 V	27.8 V	27.8 V	27.8 V
<ul> <li>at 20 °C recommended</li> </ul>	27.3 V	27.9 V	27.3 V	27.3 V	27.3 V
<ul> <li>at 30 °C recommended</li> </ul>	26.8 V	27.5 V	26.8 V	26.8 V	26.8 V
<ul> <li>at 40 °C recommended</li> </ul>	26.6 V	27.2 V	26.6 V	26.6 V	26.6 V
<ul> <li>at 50 °C recommended</li> </ul>	26.3 V	26.8 V	26.3 V	26.3 V	26.3 V
<ul> <li>at 60 °C recommended</li> </ul>	-	26.4 V	-	-	-
Output					
Permissible charging current, max.	0.3 A	5 A	0.8 A	1.75 A	3 A
Rated voltage Vout rated DC	24 V	24 V	24 V	24 V	24 V
Safety					
Short-circuit protection	Battery fuse 7.5 A/32 V (solid-state circuitry blade-type fuse + support)	Battery fuse 15 A/32 V (solid-state circuitry blade-type fuse + support)	Battery fuse 15 A/32 V (solid-state circuitry blade-type fuse + support)	Battery fuse 20 A/32 V (solid-state circuitry blade-type fuse + support)	Battery fuse 20 A/32 V (solid-state circuitry blade-type fuse + support)
Design of the overload protection	Valve control	Valve control	Valve control	Valve control	Valve control
Safety					
Protection class	Class III	Class III	Class III	Class III	Class III
Degree of protection (EN 60529)	IP00	IP00	IP00	IP00	IP00
Approvals					
CE mark	Yes	Yes	Yes	Yes	Yes
UL/cUL (CSA) approval	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627
Marine approval	DNV GL, ABS	DNV GL, ABS	DNV GL, ABS	DNV GL, ABS	DNV GL, ABS

# SITOP DC UPS uninterruptible power supplies DC UPS with battery modules

DC UPS battery modules

Article number	6EP1935-6MC01	6EP1935-6MD31	6EP1935-6MD11	6EP1935-6ME21	6EP1935-6MF01
Product	SITOP Battery module	SITOP Battery module	SITOP Battery module	SITOP Battery module	SITOP Battery modul
Product type	Battery module 1.2 Ah	Battery module 2.5 Ah	Battery module 3.2 Ah	Battery module 7 Ah	Battery module 12 A
environmental conditions		-			-
Operating data note	and operation of lead- acid batteries, the relevant DIN/VDE regulations or country- specific regulations (e.g. VDE 0510 Part 2/ EN 50272-2) must be observed. You must ensure that the battery site is sufficiently venti- lated. Possible sources of ignition	and operation of lead- acid batteries, the relevant DIN/VDE regulations or country- specific regulations (e.g. VDE 0510 Part 2/	acid batteries, the relevant DIN/VDE regulations or country- specific regulations (e.g. VDE 0510 Part 2/ EN 50272-2) must be observed. You must ensure that the battery site is sufficiently venti- lated. Possible sources of ignition	specific regulations / (e.g. VDE 0510 Part 2/ EN 50272-2) must be observed. You must ensure that the battery site is sufficiently venti- lated. Possible sources of ignition	specific regulations (e.g. VDE 0510 Part : EN 50272-2) must be observed. You must ensure that the batter site is sufficiently ver lated. Possible sources of ignition
Ambient temperature					
<ul> <li>during operation</li> </ul>	-15 +50 °C	-40 +60 °C	-15 +50 °C	-15 +50 °C	-15 +50 °C
<ul> <li>during transport</li> </ul>	-20 +50 °C	-40 +60 °C	-20 +50 °C	-20 +50 °C	-20 +50 °C
<ul> <li>during storage</li> </ul>	-20 +50 °C	-40 +60 °C	-20 +50 °C	-20 +50 °C	-20 +50 °C
Relative temporary capacity loss at 20 °C in a month typical	3 %	3 %	3 %	3 %	3 %
Service life					
Service life of energy storage					
typical Note	capacity falls to 50 % of original capacity	capacity falls to 50 % of original capacity	capacity falls to 50 % of original capacity	capacity falls to 50 % of original capacity	capacity falls to 50 % of original capacity
<ul> <li>at 20 °C typical</li> </ul>	4 у	10 y	4 y	4 y	4 у
<ul> <li>at 30 °C typical</li> </ul>	2 у	7 у	2 у	2 у	2 у
<ul> <li>at 40 °C typical</li> </ul>	1 у	3 у	1 y	1 y	1 y
<ul> <li>at 50 °C typical</li> </ul>	0.5 y	1.5 y	0.5 y	0.5 y	0.5 y
<ul> <li>at 60 °C typical</li> </ul>		1 y			
Ambient temperature during storage Note	and operating temperature, other factors such as the duration of the storage period and the charge status during storage have a decisive influence on the possible useful life. Batteries should therefore be stored as briefly as possible,	Along with the storage and operating temperature, other factors such as the duration of the storage period and the charge status during storage have a decisive influence on the possible useful life. Batteries should therefore be stored as briefly as possible, always fully charged, and within the temperature range 0 to +20 °C.	and operating temperature, other factors such as the duration of the storage period and the charge status during storage have a decisive influence on the possible useful life. Batteries should	Along with the storage and operating temperature, other factors such as the duration of the storage period and the charge status during storage have a decisive influence on the possible useful life. Batteries should therefore be stored as briefly as possible, always fully charged, and within the temperature range 0 to +20 °C.	and operating temperature, other factors such as the

# SITOP DC UPS uninterruptible power supplies

DC UPS with battery modules

### DC UPS battery modules

### **Technical specifications** (continued)

Article number	6EP1935-6MC01	6EP1935-6MD31	6EP1935-6MD11	6EP1935-6ME21	6EP1935-6MF01
Product	SITOP Battery module				
Product type	Battery module 1.2 Ah	Battery module 2.5 Ah	Battery module 3.2 Ah	Battery module 7 Ah	Battery module 12 Ah
Mechanics					
Connection technology	spring-loaded terminals	spring-loaded terminals	spring-loaded terminals	spring-loaded terminals	spring-loaded terminals
Connection for power supply unit	1 screw terminal each for 0.08 2.5 mm <sup>2</sup> for + BAT and - BAT	1 screw terminal each for 0.08 2.5 mm <sup>2</sup> for + BAT and - BAT		1 screw terminal each for 0.08 4 mm <sup>2</sup> for + BAT and - BAT	1 screw terminal each for 0.08 4 mm <sup>2</sup> for + BAT and - BAT
Product component belonging to	Accessories pack with solid-state circuitry fuse 7.5 A	Accessories pack with solid-state circuitry fuse 15 A	Accessories pack with solid-state circuitry fuse 15 A	Accessories pack with solid-state circuitry fuse 20 A and 30 A	Accessories pack with solid-state circuitry fuse 20 A and 30 A
Width of the enclosure	96 mm	265 mm	190 mm	186 mm	253 mm
Height of the enclosure	106 mm	151 mm	151 mm	168 mm	168 mm
Depth of the enclosure	108 mm	91 mm	82 mm	121 mm	121 mm
Installation width	116 mm	285 mm	210 mm	206 mm	273 mm
Installation height	126 mm	171 mm	171 mm	188 mm	188 mm
Weight, approx.	1.8 kg	3.8 kg	3.2 kg	6 kg	9 kg
Installation	snaps onto DIN rail EN 60715 35x7.5/15 or keyhole mounting for hooking in to M4 screws	snaps onto DIN rail EN 60715 35x15 or keyhole mounting for hooking in to M4 screws	snaps onto DIN rail EN 60715 35x7.5/15 or keyhole mounting for hooking in to M4 screws	can be screwed onto flat surface (keyhole mounting for hooking in to M4 screws)	can be screwed onto flat surface (keyhole mounting for hooking in to M4 screws)
Number of cells	12	12	12	12	12
Battery	1.2 A·h	2.5 A·h	3.2 A·h	7 A·h	12 A·h
Reference code acc. to DIN EN 81346-2	G	G	G	G	G
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

# Ar

Ordering data

Battery module 1.2 Ah for DC UPS module 6 A

Battery module 2.5 Ah

Battery module 3.2 Ah

for DC UPS modules 6 A and 15 A

for DC UPS modules 6 A and 15 A

Article No.

6EP1935-6MC01

6EP1935-6MD31

6EP1935-6MD11

#### Article No.

Battery module 7 Ah	6EP1935-6ME21
 for DC UPS modules 6 A, 15 A and 40 A	
Battery module 12 Ah	6EP1935-6MF01
for DC UPS modules 6 A, 15 A and 40 A	

© Siemens 2019

# Add-on modules





- Introduction Redundancy module
- **9/2** 9/3
- Selectivity module Buffer module
- Inrush current limiter

### Introduction


### Overview



#### Expansion modules for increasing system availability

A power supply unit on its own cannot guarantee fault-free 24 V supply. Power failures, extreme variations in the mains voltage, or a faulty load can bring plant operation to a standstill and cause high costs. The add-on modules offer everything from extensive protection against interference on the primary and secondary side right up to complete all-round protection.

#### Redundancy modules – for doubling system availability




SITOP redundancy module

Advantages of the redundancy modules

- High availability of the 24 V supply thanks to redundant configuration
- · Power is reliably supplied even when a power supply fails
- Compact redundancy modules for power supplies up to 40 A
- Redundancy module 24 V/NEC Class 2 with limiting to 100 VA
- Diagnostics messages via LED and signaling contacts with SITOP PSE202U
- Adjustable switching threshold for LED and signaling contacts with SITOP PSE202U

#### Selectivity modules – for protection of 24 V feeds




SITOP selectivity module

#### Advantages of selectivity modules

- Reliable detection of overload or short-circuit in the 24 V circuit
- Reliable shutdown in case of overload regardless of cable lengths or cross-sections
- Choice of eight or four load feeders per module
- Versions with adjustable thresholds from 0.5 to 3 A, 2 to 10 A, or 3 to 10 A
- Sequential connection of feeds is possible to reduce inrush current
- Diagnostics via group signaling contact or single-channel signaling
- Evaluation via free-of-charge SIMATIC S7 function blocks for modules with single-channel signaling

#### Buffer module - bridging power failures for as long as seconds




SITOP buffer module

Advantages of the buffer module

Power failures normally only last for fractions of a second, but they can still cause costly and time-consuming damage in sensitive production areas. In combination with SITOP smart and SITOP modular power supply units, the buffer module bridges short voltage dips of this type with its electrolytic capacitors and ensures uninterrupted operation.

Inrush current limiter: Protection of downstream power supplies against excessively high inrush currents



Advantages of inrush current limiters:

- Maximum service life of current sensitive components (e.g. relays) by reducing inrush currents
- Space savings thanks to narrow width of 18 mm
- Matching LOGO! modules and sub-distribution boards through staggered profile
- Flexible installation on DIN rail, as wall mounting or in various other installation positions
- Maximum plant configuration enables flexible application possibilities at temperatures from -40 °C to +70 °C

### More information

Select the appropriate power supply quickly and easily with the SITOP Selection Tool: http://www.siemens.com/tst

### Overview



The SITOP redundancy modules are the optimal extension for all 24 V power supplies to ensure additional protection from failure of the 24 V supply. The redundancy module continuously monitors the power supply units and, in the event that one unit fails, the other unit automatically takes over the 24 V power supply. With the SITOP PSE202U redundancy modules, a signal is additionally sent via a signaling contact that can then easily be evaluated by a controller, PC, or control system. With the SITOP RED1200 redundancy modules, this message can be implemented in the form of a missing signal from the defective power supply.

### Benefits


- High availability of the 24 V supply thanks to redundant configuration
- Power is reliably supplied even when a power supply fails
- Compact redundancy modules for power supplies up to 40 A
- Redundancy module 24 V/NEC Class 2 with limiting to 100 VA
- Diagnostics messages via LED and signaling contacts with SITOP PSE202U
- Adjustable switching threshold for LED and signaling contacts with SITOP PSE202U

### Application

The redundancy module decouples two 24 V power supplies of the same type so that the loads are still supplied by the second power supply (1 + 1 redundancy) in case one of the two power supplies fails.

Redundancy modules support parallel switching of power supplies of the same type to increase performance while offering redundancy at the same time (N + 1 redundancy).

You can use the NEC Class 2 redundancy module to implement a redundant 24 V supply limited to an output power of 100 VA.



#### Design

For redundant configuration of a 24 V supply, the redundancy module decouples two SITOP 24 V power supplies of the same type by means of diodes in parallel operation. Depending on the output current of the power supplies, 1 to 2 redundancy modules may be required.

### Function

#### Monitoring

The redundancy module continuously monitors the output voltage of the connected power supplies. The switching threshold of 20 to 25 V can be set on the device. A signal indicates if the output voltage of one of the two power supplies sinks to the set value or below.

#### SITOP PSE202U redundancy module signaling

The LED on the device and a changeover contact signal a faulty power supply.

The signal evaluation of the PSE202U is also represented in our library for SIMATIC PCS 7. Download: https://support.industry.siemens.com/cs/ww/en/view/109476154

9

# Redundancy module

# Technical specifications

Article number	6EP4346-7RB00-0AX0	6EP4347-7RB00-0AX0	6EP1962-2BA00	6EP1964-2BA00	6EP1961-3BA21
Product	RED1200 2x10A	RED1200 2x20A	SITOP PSE202U	SITOP PSE202U	SITOP PSE202U
Input					
Input	DC voltage	DC voltage	DC voltage	DC voltage	DC voltage
Supply voltage					
• at DC	12 48 V	12 48 V	24 24 V	24 24 V	24 24 V
Input voltage					
• at DC	10 58 V	10 58 V	19 29 V	19 29 V	24 28.8 V
Output					
Output	Controlled DC voltage	Controlled DC voltage	Controlled, isolated	Controlled, isolated	Controlled, isolated
			DC voltage	DC voltage	DC voltage
Number of outputs	1	1			
Rated voltage Vout rated DC	24 V	24 V	24 V	24 V	24 V
Output voltage	V <sub>in</sub> - approx. 0.6 V	V <sub>in</sub> - approx. 0.6 V	V <sub>in</sub> - approx. 0.5 V	V <sub>in</sub> - approx. 0.5 V	V <sub>in</sub> - approx. 0.5 V
Product function Output voltage	No	No	No	No	No
adjustable					
Status display	-	-	Green LED for "both input voltages > switching threshold"; red LED for "at least one input voltage < switching threshold" or "output switched off"	Green LED for "both Input voltages > switching threshold"; red LED: for "at least one input voltage < switching threshold"	Green LED for "both Input voltages > switching threshold"; red LED: for "at least one input voltage < switching threshold"
Signaling	-	-	Isolated relay contact (contact rating 6 A/42 V AC, 30 V DC, but max. 100 VA): Contact closed if one or both input voltages < switching threshold or output is switched off. Setting range of switching threshold 20 V ±0.5 V to 25 V ±0.5 V	Isolated relay contact (contact rating 6  A/42  V AC, $30  V DC$ ): Contact closed if both input voltages > switching threshold, setting range of switching threshold $20 \text{ V} \pm 0.5 \text{ V}$ to $25 \text{ V} \pm 0.5 \text{ V}$	Isolated relay contact (changeover contacts, rating 8 A/240 V AC, 24 V DC): Signals OK if both input voltages > switching threshold, setting range of threshold 20 25 V
Rated current value Iout rated	20 A	40 A	3.8 A	10 A	40 A
Current range	-	-	4.6 A	10 A	40 A
Note		-	Maximum aggregate current in the event of an error according to NEC class 2 limit 8 A	max. aggregate current 10 A	max. aggregate current 40 A; +60 +70 °C: derating 3%/K
Efficiency					
Efficiency at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	97.5 %	97.5 %	94.8 %	97.1 %	96.6 %
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	12 W	25 W	5 W	3.6 W	34 W
Power loss [W] during no-load operation maximum	0.1 W	0.1 W	2 W	1 W	1.5 W
Safety					
Primary/secondary isolation	No	No			
Galvanic isolation Protection class	- Class III	- Class III	yes, SELV acc. to EN 60950-1 (relay contact) Class III	yes, SELV acc. to EN 60950-1 (relay contact) Class III	yes, SELV acc. to EN 60950-1 (relay contact) Class I
CE mark	Yes	Yes	Yes	Yes	Yes
UL/cUL (CSA) approval		cULus-Listed (UL 508,		cULus-Listed (UL 508,	
	CSA C22.2 No. 107.1), File E197259		CSA C22.2 No. 107.1), File E197259; UL-Recognized (UL 60950-1, NEC class 2), File E151273		CSA C22.2 No. 107.1), File E197259
Explosion protection		-	-	-	IECEX EX NA NC IIC T4 Gc; ATEX (EX) II 3G EX NAC IIC T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4
FM approval	-	-	-	-	-
CB approval	-	-	No	No	
Marine approval	-	-	-	-	ABS, DNV GL
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20	IP20

# Redundancy module

Article number	6EP4346-7RB00-0AX0	6EP4347-7RB00-0AX0	6EP1962-2BA00	6EP1964-2BA00	6EP1961-3BA21
Product	RED1200 2x10A	RED1200 2x20A	SITOP PSE202U	SITOP PSE202U	SITOP PSE202U
EMC					
Emitted interference	EN 61000-6-3	EN 61000-6-3	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
Noise immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data					
Ambient temperature					
<ul> <li>during operation</li> </ul>	-25 +70 °C	-25 +70 °C	-20 +70 °C	-20 +70 °C	-25 +70 °C
- Note	with natural convection	with natural convection	with natural convection	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics					
Connection technology	Push-in terminals	Push-in terminals	screw-type terminals	screw-type terminals	screw-type terminals
Connections					
Supply input	In1, In2: 0.5 6 mm² each	In1, In2: 0.5 16 mm <sup>2</sup> each	Input, output and ground: removable screw terminal, each 1 x 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	Input, output and ground: removable screw terminal, each 1 x 0.5 2.5 mm <sup>2</sup> single-core/finely stranded	Input, output and ground: 1 screw terminal each for 0.33 10 mm <sup>2</sup> single-core/finely stranded
Output	Out1: 0.5 6 mm <sup>2</sup>	Out1: 0.5 16 mm <sup>2</sup>			
Auxiliary	-	-	Relay contact: 2 screw terminals for 0.5 2.5 mm <sup>2</sup> single- core/finely stranded	Relay contact: 2 screw terminals for 0.5 2.5 mm <sup>2</sup> single- core/finely stranded	Relay contact: 3 screw terminals for 0.5 2.5 mm <sup>2</sup> single core/finely stranded
Width of the enclosure	35 mm	45 mm	30 mm	30 mm	70 mm
Height of the enclosure	135 mm	135 mm	80 mm	80 mm	125 mm
Depth of the enclosure	125 mm	125 mm	100 mm	100 mm	125 mm
Required spacing					
• top	45 mm	45 mm	50 mm	50 mm	50 mm
bottom	45 mm	45 mm	50 mm	50 mm	50 mm
• left	0 mm	0 mm	0 mm	0 mm	0 mm
• right	0 mm	0 mm	0 mm	0 mm	0 mm
Weight, approx.	0.47 kg	0.51 kg	0.125 kg	0.125 kg	0.5 kg
Product feature of the enclosure housing for side-by-side mounting	Yes	Yes	Yes	Yes	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
Electrical accessories	-	-	Removable spring- type terminal 6EP1971-5BA00	Removable spring- type terminal 6EP1971-5BA00	-
MTBF at 40 °C	8 100 000 h	6 100 000 h	678 210 h	3 273 000 h	6 471 654 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rate input voltage and ambient temperature +25 °C (unless otherwise specified)

ordering data	Article No.	Accessories	Article No.
ITOP RED1200 edundancy module	6EP4346-7RB00-0AX0	Device identification labels	3RT2900-1SB20
nput/output:		For SITOP RED1200:	
12 V DC, 24 V, 48 V/20 A Suitable for decoupling two		SIMATIC ET 200SP labels	6ES7193-6LF30-0AW0
SITOP power supplies with a maximum of 10 A output current each		160 equipment labeling plates, 10 sheets (160 plates)	
SITOP RED1200 edundancy module	6EP4347-7RB00-0AX0		
nput/output: 12 V DC, 24 V, 48 V/40 A			
Suitable for decoupling two			
SITOP power supplies with a maximum of 20 A output current each			
SITOP PSE202U edundancy module	6EP1961-3BA21		
nput/output:			
24 V DC/40 A Suitable for decoupling two			
SITOP power supplies with a maximum of 20 A output current			
SITOP PSE202U	6EP1962-2BA00		
edundancy module			
nput/output: 24 V DC/NEC Class 2			
Suitable for decoupling two SITOP power supplies output			
power limited < 100 VA			
SITOP PSE202U edundancy module	6EP1964-2BA00		
nput/output:			
24 V DC/10 A Suitable for decoupling two			
SITOP power supplies with a naximum of 5 A output current			

### Overview



#### Selectivity and rapid fault localization in 24 V feeders

The SITOP PSE200U, SITOP select and SITOP SEL1200/-1400 selectivity modules are the optimal expansion for all 24 V power supplies in order to distribute and monitor the load current across multiple feeders. Overload and short-circuit in one or more feeders is reliably detected and signaled.


The electronics permit brief current peaks caused, for example, by high inrush currents, but disconnects feeders in the event of an extended overload. This is ensured even on high-resistance lines and in the case of "creeping" short-circuits. In such cases, miniature circuit breakers fail to trip, or trip too late, even if the power supply unit could deliver the required tripping current. The SITOP expansion module continues to supply the intact feeders with 24 V absolutely free of interruptions and feedback – a feature which avoids a possible total system failure.

### Benefits

- Reliable shutdown in case of overload regardless of cable lengths or cable cross-sections
- Choice of 4 or 8 load feeders per module with individually adjustable response threshold from 0.5–3 A, 2–10 A or 3–10 A for each output
- Voltage measuring points for output currents (1 V = 1 A), disconnection of load circuit is not required
- Two options for remote diagnostics: Group signaling contact or single-channel signaling
- Versions with power limitation of the outputs to 100 VA according to NEC Class 2
- Evaluation via free-of-charge SIMATIC S7 or SIMOTION function blocks (S7-1500/1200/300/400) or via LOGO! Software for modules with single-channel signaling (PSE200U)
- Simple configuration thanks to individual setting of maximum current for every output using potentiometers
- 3-color LEDs for fast on-site fault localization
- Remote reset possible from a central location (PSE200U, SEL1200/-1400)
- Simple commissioning thanks to manual switch on/off of outputs (PSE200U, SEL1200/-1400)
- Sequential connection of feeders to reduce total inrush current
- Sealable transparent cover over adjusters for currents and times protects against maladjustment (PSE200U, SEL1200/-1400)
- Library for visualization in SIMATIC PCS 7

#### Application

The selectivity module is used in conjunction with 24 V power supplies to distribute the load current over several feeders and to monitor the individual currents. Faults in individual circuits caused by overload or short-circuit are detected and selectively switched off so that further load current paths remain unaffected by the fault. This achieves fast fault diagnostics and minimizes downtimes.



### Design

The selectivity module is specially designed for the response of switched-mode power supply units and the 24 V DC feeders to be supplied. Individual setting of the response threshold allows optimum adaptation to the respective feeder.

### Selectivity module

### Function

#### Monitoring

The current per output is monitored by the selectivity modules; if the set threshold of the output is exceeded, the output is switched off according to a predefined time-current characteristic curve. In addition, the supplying 24 V input voltage is constantly being monitored. As soon as this voltage threatens to fail, the path with a higher current than the set threshold is disconnected immediately. All other feeders continue to be supplied without interruption.

### Signaling

Signaling of the faulty feeder takes place by the LEDs on the device as well as via group signaling contact or single-channel signaling. The selectivity module with its single-channel signaling option outputs the status of the individual outputs cyclically, by means of a serial code which can be read in by a digital PLC input.

Free function blocks for SIMATIC S7-300/400/1200/1500 for STEP 7 and TIA Portal as well as SIMOTION CPUs with SIMOTION SCOUT are available for evaluation. This enables simple integration into the S7 diagnostics and host control or HMI systems. The integration into the LOGO! logic module is also an application example.

More information, as well as the function blocks for download, can be found at:

#### SIMATIC S7:

http://support.automation.siemens.com/WW/view/en/61450284

### SIMOTION:

http://support.automation.siemens.com/WW/view/en/82555461

#### http://www.siemens.com/logo-application-examples

Easy visualization in the SIMATIC PCS 7 process control system is made possible by the SITOP library, which contains the function blocks and faceplates for individual channel and common signaling:

http://support.industry.siemens.com/cs/ww/en/view/109476154

### Connecting and disconnecting the outputs

During device startup you can select between simultaneous connection of all outputs, as well as sequential connection or load-dependent connection in order to reduce the peak inrush currents.

Each output can be manually connected and disconnected on the device (for example, for commissioning or service). Disconnected outputs can be connected by means of remote reset (24 V input). Prerequisite is that the outputs were not disconnected manually on the device.

#### Switch-off characteristic

The SITOP PSE200U, SITOP select and SITOP SEL1400 redundancy modules feature a limiting switch-off characteristic, whereas the SITOP SEL1200 redundancy modules have a switching one. The SITOP SEL1200 is adequate for all load components which correspond to the PLC standard. With this module, the voltage can briefly drop below 20 V. The SITOP SEL1400 prevents voltage drops below 20 V in the loads and therefore also protects those components which do not correspond to the PLC standard.

#### Technical specifications

Article number	6EP4438-7FB00-3DX0	6EP4438-7EB00-3DX0
Product brand name	SITOP SEL1200	SITOP SEL1400
Type of current supply	Selectivity module, 8 x 2 10 A Common signal contact or diagnostic monitor	Selectivity module, 8 x 2 10 A Common signal contact or diagnostic monitor
Input		
Type of the power supply network	Controlled DC voltage	Controlled DC voltage
Supply voltage at DC Rated value	24 V	24 V
Input voltage at DC	20.4 30 V	20.4 30 V
Overvoltage overload capability	35 V	35 V
Input current at rated input voltage 24 V Rated value	60 A	60 A
Output		
Voltage curve at output	controlled DC voltage	controlled DC voltage
Formula for output voltage	V <sub>in</sub> - approx. 0.2 V	V <sub>in</sub> - approx. 0.2 V
Relative overall tolerance of the voltage Note	In accordance with the supplying input voltage	In accordance with the supplying input voltage
Number of outputs	8	8
Output current up to 60 °C per output rated value	10 A	10 A
Adjustable pick-up value current of the current-dependent overload release	2 10 A	2 10 A
Type of response value setting	via potentiometer	via potentiometer
Product feature parallel switching of outputs	Yes	Yes
Product feature bridging of equipments	No	No

Article number	6EP4438-7FB00-3DX0	6EP4438-7EB00-3DX0
Product brand name	SITOP SEL1200	SITOP SEL1400
Type of current supply	Selectivity module, 8 x 2 10 A Common signal contact or diagnostic monitor	Selectivity module, 8 x 2 10 A Common signal contact or diagnostic monitor
Efficiency		
Efficiency in percent	98 %	98 %
Power loss [W] at rated output curren for rated value of the output current typical	t 18 W	18 W
Switch-off characteristic per output		
Switching characteristic		
<ul> <li>of the excess current</li> </ul>	lout = 1.01.5 x set value, switch-off after approx. 5 s	$l_{out} = 1.0 \dots 1.5 \text{ x}$ set value, switch-off after approx. 5 s
<ul> <li>of the current limitation</li> </ul>	lout = 1.5 x set value, switch-off after typ. 1 s	$l_{out} = 1.5 \text{ x set value, switch-off after typ. 100 ms}$
of the immediate switch-off	$l_{\rm out}$ > set value and $V_{\rm in}$ < 20 V, switch-off after approx. 8 ms	$I_{\rm out}>$ set value and $V_{\rm in}<$ 20 V, switch-off after approx. 0.5 ms
Design of the reset device/resetting mechanism	via sensor per output	via sensor per output
Remote reset function	Non-electrically isolated 24 V input (signal level "high" at > 15 V)	Non-electrically isolated 24 V input (signal level "high" at > 15 V)
Protection and monitoring		
Display version for normal operation	Three-color LED per output: green LED for "Output switched through"; yellow LED for "Output switched off manually"; red LED for "Output switched off due to overcurrent"	Three-color LED per output: green LED for "Output switched through"; yellow LED for "Output switched off manually"; red LED for "Output switched off due to overcurrent"
Safety		
Galvanic isolation between input and output at switch-off	No	No
Operating resource protection class	Class III	Class III
Certificate of suitability		
<ul> <li>CE marking</li> </ul>	Yes	Yes
<ul> <li>as approval for USA</li> </ul>	UL-Recognized (UL 2367) File E328600; cULus-Listed (UL 508, CSA C22.2 No. 107.1) File E197259	UL-Recognized (UL 2367) File E328600; cULus-Listed (UL 508, CSA C22.2 No. 107.1) File E197259
Standard for safety	according to EN 60950-1 and EN 50178	according to EN 60950-1 and EN 50178
Protection class IP	IP20	IP20
EMC		
Standard		
<ul> <li>for emitted interference</li> </ul>	EN 61000-6-3	EN 61000-6-3
<ul> <li>for interference immunity</li> </ul>	EN 61000-6-2	EN 61000-6-2
Operating data		
Ambient temperature		
<ul> <li>during operation</li> </ul>	-25 +60 °C	-25 +60 °C
- Note	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C	-40 +85 °C
Environmental category acc. to IEC 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics		
Width of the enclosure	45 mm	45 mm
Height of the enclosure	135 mm	135 mm
Depth of the enclosure	125 mm	125 mm
Installation width	45 mm	45 mm
Mounting height	225 mm	225 mm
Net weight	0.3 kg	0.4 kg
Mounting type	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
MTBF at 40 °C	925 000 h	363 000 h
Other information	Specifications at rated input voltage and ambient	Specifications at rated input voltage and ambient

# Selectivity module

## Technical specifications (continued)

Article number	6EP1961-2BA11	6EP1961-2BA31	6EP1961-2BA51	6EP1961-2BA61
Product brand name	SITOP PSE200U	SITOP PSE200U	SITOP PSE200U	SITOP PSE200U
Type of current supply	Selectivity module, 4 x 3 A Common signal contact	Selectivity module, 4 x 3 A Single-channel signaling	Selectivity module, 4 x 3 A NEC Class 2, Common signal contact	Selectivity module, 4 x 3 A NEC Class 2, Single-channel signaling
Input				
Type of the power supply network	Controlled DC voltage	Controlled DC voltage	Controlled DC voltage	Controlled DC voltage
Supply voltage at DC Rated value	24 V	24 V	24 V	24 V
Input voltage at DC	22 30 V	22 30 V	22 30 V	22 30 V
Overvoltage overload capability	35 V	35 V	35 V	35 V
Input current at rated input voltage 24 V Rated value	12 A	12 A	12 A	12 A
Output				
Voltage curve at output	controlled DC voltage	controlled DC voltage	controlled DC voltage	controlled DC voltage
Formula for output voltage	V <sub>in</sub> - approx. 0.2 V	V <sub>in</sub> - approx. 0.2 V	V <sub>in</sub> - approx. 0.2 V	V <sub>in</sub> - approx. 0.2 V
Relative overall tolerance of the	In accordance with the	In accordance with the	In accordance with the	In accordance with the
voltage Note	supplying input voltage	supplying input voltage	supplying input voltage	supplying input voltage
Number of outputs Output current up to 60 °C per	4 3 A	4 3 A	4 3 A	4 3 A
output rated value			0.5 3 A	0.5 3 A
Adjustable pick-up value current of the current-dependent overload release	0.5 3 A	0.5 3 A	0.5 3 A	0.5 3 A
Type of response value setting	via potentiometer	via potentiometer	via potentiometer	via potentiometer
Product feature parallel switching of outputs	No	No	No	No
Product feature bridging of equipments	Yes	Yes	Yes	Yes
Type of outputs connection	Simultaneous connection of all outputs after power up of the supply voltage > 20 V, delay time of 25 ms, 100 ms or adjustable "load optimised" via DIP switch for sequential connection	Simultaneous connection of all outputs after power up of the supply voltage > 20 V, delay time of 25 ms, 100 ms or adjustable "load optimised" via DIP switch for sequential connection	Simultaneous connection of all outputs after power up of the supply voltage > 20 V, delay time of 25 ms, 100 ms or adjustable "load optimised" via DIP switch for sequential connection	Simultaneous connection of all outputs after power up of the supply voltage > 20 V, delay time of 25 ms, 100 ms or adjustable "load optimised" via DIP switch for sequential connection
Efficiency				
Efficiency in percent	97 %	97 %	97 %	97 %
Power loss [W] at rated output current for rated value of the output current typical	9 W	9 W	9 W	9 W
Switch-off characteristic per output				
Switching characteristic				
of the excess current	<i>l</i> <sub>out</sub> = 1.01.5 x set value, switch-off after approx. 5 s	$l_{out} = 1.0 \dots 1.5 x$ set value, switch-off after approx. 5 s	$I_{out} = 1.0 \dots 1.1 \text{ x set value},$ switch-off after approx. 5 s	<i>I</i> <sub>out</sub> = 1.01.1 x set value, switch-off after approx. 5 s
of the current limitation	<i>I</i> <sub>out</sub> = 1.5 x set value, switch-off after typ. 100 ms	<i>I</i> <sub>out</sub> = 1.5 x set value, switch-off after typ. 100 ms	<i>I</i> <sub>out</sub> = 1.1 x set value, switch-off after typ. 100 ms	<i>I</i> <sub>out</sub> = 1.1 x set value, switch-off after typ. 100 ms
of the immediate switch-off	l <sub>out</sub> > set value and Vin < 20 V, switch-off after approx. 0.5 ms	<i>I</i> <sub>out</sub> > set value and Vin < 20 V, switch-off after approx. 0.5 ms	<i>I</i> <sub>out</sub> > set value and Vin < 20 V, switch-off after approx. 0.5 ms	<i>l</i> <sub>out</sub> > set value and Vin < 20 V, switch-off after approx. 0.5 ms
Residual current at switch-off typical	1 mA	1 mA	1 mA	1 mA
Design of the reset device/resetting mechanism	via sensor per output	via sensor per output	via sensor per output	via sensor per output
Remote reset function	Non-electrically isolated 24 V input (signal level "high" at > 15 V)	Non-electrically isolated 24 V input (signal level "high" at > 15 V)	Non-electrically isolated 24 V input (signal level "high" at > 15 V)	Non-electrically isolated 24 V input (signal level "high" at > 15 V)
Protection and monitoring				
Fuse protection type at input	5 A per output	5 A per output	5 A per output	5 A per output
Display version for normal operation	(not accessible) Three-color LED per output: green LED for "Output switched through"; yellow	(not accessible) Three-color LED per output: green LED for "Output switched through"; yellow LED for "Output switched off manually"; red LED for "Output switched off due to overcurrent"	(not accessible) Three-color LED per output: green LED for "Output switched through"; yellow LED for "Output switched off manually"; red LED for "Output switched off due to overcurrent"	(not accessible) Three-color LED per output: green LED for "Output switched through"; yellow
Design of the switching contact for signaling function	Common signal contact (changeover contact, rating 0.1 A/24 V DC)	Status signal output (pulse/ pause signal, can be evaluated via Simatic function block)	Common signal contact (changeover contact, rating 0.1 A/24 V DC)	Status signal output (pulse/ pause signal, can be evaluated via Simatic function block)

Article number Product brand name Type of current supply	6EP1961-2BA11 SITOP PSE200U Selectivity module, 4 x 3 A Common signal contact	6EP1961-2BA31 SITOP PSE200U Selectivity module, 4 x 3 A Single-channel signaling	6EP1961-2BA51 SITOP PSE200U Selectivity module, 4 x 3 A NEC Class 2, Common signal contact	6EP1961-2BA61 SITOP PSE200U Selectivity module, 4 x 3 NEC Class 2, Single-channel signalin
Safety				
Galvanic isolation between input and output at switch-off	No	No	No	No
Operating resource protection class Certificate of suitability	Class III	Class III	Class III	Class III
CE marking	Yes	Yes	Yes	Yes
• as approval for USA	UL-Recognized (UL 2367) File E328600; cULus-Listed (UL 508, CSA C22.2 No. 107.1) File E197259	UL-Recognized (UL 2367) File E328600; cULus-Listed (UL 508, CSA C22.2 No. 107.1) File E197259	UL-Recognized (UL 2367) File E328600; cULus-Listed (UL 508, CSA C22.2 No. 107.1) File E197259; NEC Class2 (UL1310)	UL-Recognized (UL 236; File E328600; cULus-List (UL 508, CSA C22.2 No. 107.1) File E197259; NEC Class2 (UL1310)
Standard for safety	according to EN 60950-1 and EN 50178	according to EN 60950-1 and EN 50178	according to EN 60950-1 and EN 50178	according to EN 60950- and EN 50178
Certificate of suitability relating to ATEX	IECEX EX NA NC IIC T4 GC; ATEX (EX) II 3G EX NA NC IIC T4 GC; CULUS Class I, Div. 2, Group ABCD, T4	CULus Class I, Div. 2, Group ABCD, T4	ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cULus Class I, Div. 2, Group ABCD, T4	cULus Class I, Div. 2, Group ABCD, T4
Shipbuilding approval	DNV GL, ABS	DNV GL, ABS	DNV GL, ABS	DNV GL, ABS
Protection class IP	IP20	IP20	IP20	IP20
EMC				
Standard				
for emitted interference	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
for interference immunity	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data				
Ambient temperature				
during operation	-25 +60 °C	-25 +60 °C	-25 +60 °C	-25 +60 °C
- Note	with natural convection	with natural convection	with natural convection	with natural convection
during transport	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
during storage	-40 +85 °C	-40 +85 °C	-40 +85 °C	-40 +85 °C
Environmental category acc. to IEC 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics				
Type of electrical connection	screw-type terminals	screw-type terminals	screw-type terminals	screw-type terminals
• at input	+24 V: 2 screw terminals for 0.5 16 mm <sup>2</sup> ; 0 V: 2 screw terminals for 0.5 4 mm <sup>2</sup>	+24 V: 2 screw terminals for 0.5 16 mm <sup>2</sup> ; 0 V: 2 screw terminals for 0.5 4 mm <sup>2</sup>	+24 V: 2 screw terminals for 0.5 16 mm <sup>2</sup> ; 0 V: 2 screw terminals for 0.5 4 mm <sup>2</sup>	+24 V: 2 screw terminals 0.5 16 mm <sup>2</sup> ; 0 V: 2 scr terminals for 0.5 4 mn
at output	Output 1 4: 1 screw terminal each for 0.5 4 mm <sup>2</sup>	Output 1 4: 1 screw terminal each for 0.5 4 mm <sup>2</sup>	Output 1 4: 1 screw terminal each for 0.5 4 mm <sup>2</sup>	Output 1 4: 1 screw terminal each fo 0.5 4 mm <sup>2</sup>
<ul> <li>for signaling contact</li> </ul>	3 screw terminals for 0.5 4 mm <sup>2</sup>	1 screw terminal for 0.5 4 mm <sup>2</sup>	3 screw terminals for $0.5 \dots 4 \text{ mm}^2$	1 screw terminal for 0.5 4 mm <sup>2</sup>
<ul> <li>for auxiliary contacts</li> </ul>	Remote reset: 1 screw terminal for 0.5 4 mm <sup>2</sup>	Remote reset: 1 screw terminal for 0.5 4 mm <sup>2</sup>	Remote reset: 1 screw terminal for 0.5 4 mm <sup>2</sup>	Remote reset: 1 screw terminal for 0.5 4 mm <sup>2</sup>
Width of the enclosure	72 mm	72 mm	72 mm	72 mm
Height of the enclosure	80 mm	80 mm	80 mm	80 mm
Depth of the enclosure	72 mm	72 mm	72 mm	72 mm
Installation width	72 mm	72 mm	72 mm	72 mm
Mounting height	180 mm	180 mm	180 mm	180 mm
Net weight	0.2 kg	0.2 kg	0.2 kg	0.2 kg
Mounting type	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
Mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification lab 20 mm × 7 mm, TI-grey 3RT2900-1SB20
MTBF at 40 °C	755 915 h	755 915 h	755 915 h	755 915 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated in voltage and ambient temperature +25 °C (unl otherwise specified)

9

# Selectivity module

Technical specifications (continued)

Article number	6EP1961-2BA21	6EP1961-2BA41	6EP1961-2BA00
Product brand name	SITOP PSE200U	SITOP PSE200U	SITOP select
Type of current supply	Selectivity module, 4 x 10 A Common signal contact	Selectivity module, 4 x 10 A Single- channel signaling	Diagnosis module, 4 x 10 A
nput			
Type of the power supply network	Controlled DC voltage	Controlled DC voltage	Controlled DC voltage (SITOP select is not designed for operation with DC UPS module 40 A (6EP1 931-2FC21/-2FC42)
Supply voltage at DC Rated value	24 V	24 V	24 V
Input voltage at DC	22 30 V	22 30 V	22 30 V
Overvoltage overload capability	35 V	35 V	35 V; 100 ms
Input current at rated input voltage 24 V Rated value	40 A	40 A	40 A
Output			
Voltage curve at output	controlled DC voltage	controlled DC voltage	controlled DC voltage
Formula for output voltage	V <sub>in</sub> - approx. 0.2 V	V <sub>in</sub> - approx. 0.2 V	V <sub>in</sub> - approx. 0.3 V
Relative overall tolerance of the voltage Note		In accordance with the supplying input voltage	
Number of outputs	4	4	4
Output current up to 60 °C per output rated value	10 A	10 A	10 A
Adjustable pick-up value current of the current-dependent overload release	3 10 A	3 10 A	2 10 A
Type of response value setting	via potentiometer	via potentiometer	via potentiometer
Product feature parallel switching of outputs	No	No	No
Product feature bridging of equipments	Yes	Yes	Yes
Type of outputs connection	Simultaneous connection of all outputs after power up of the supply voltage > 20 V, delay time of 25 ms, 100 ms or adjustable "load optimised" via DIP switch for sequential connection	Simultaneous connection of all outputs after power up of the supply voltage > 20 V, delay time of 25 ms, 100 ms or adjustable "load optimised" via DIP switch for sequential connection	Simultaneous connection of all outputs after power up of the supply voltage, delay time of 24 ms or 100 ms programmable for sequential connection
Efficiency			
Efficiency in percent	99 %	99 %	97 %
Power loss [W] at rated output current for rated value of the output current typical	10 W	10 W	30 W
Switch-off characteristic per output			
Switching characteristic			
of the excess current	<i>I</i> <sub>out</sub> = 1.01.5 x set value, switch-off after approx. 5 s	l <sub>out</sub> = 1.01.5 x set value, switch-off after approx. 5 s	<i>I</i> <sub>out</sub> = 1.01.3 x set value, switch-off after approx. 5 s
of the current limitation	<i>l</i> <sub>out</sub> = 1.5 x set value, switch-off after typ. 100 ms	l <sub>out</sub> = 1.5 x set value, switch-off after typ. 100 ms	<i>I</i> <sub>out</sub> = 1.3 x set value, switch-off after approx. 50 100 ms
of the immediate switch-off	l <sub>out</sub> > set value and Vin < 20 V, switch-off after approx. 0.5 ms	<i>l</i> <sub>out</sub> > set value and Vin < 20 V, switch-off after approx. 0.5 ms	$l_{\rm out}$ > set value and Vin < 20 V, switch-off after approx. 0.5 ms
Residual current at switch-off typical	1 mA	1 mA	20 mA
Design of the reset device/resetting mechanism	via sensor per output	via sensor per output	Using keys on the module
Remote reset function	Non-electrically isolated 24 V input (signal level "high" at > 15 V)	Non-electrically isolated 24 V input (signal level "high" at > 15 V)	-
Protection and monitoring			
Fuse protection type at input	15 A per output (not accessible)	15 A per output (not accessible)	Blade-type fuse per output (equipped when delivered with 15 A fuse)
Display version for normal operation	for "Output switched through"; yellow LED for "Output switched off manually";	Three-color LED per output: green LED for "Output switched through"; yellow LED for "Output switched off manually"; red LED for "Output switched off due to overcurrent"	for "Output switched through"; red LED for "Output switched off due to
Design of the switching contact for signaling function	Common signal contact (changeover contact, rating 0.1 A/24 V DC)	Status signal output (pulse/pause signal, can be evaluated via Simatic function block)	Common signal contact (NO contact, rating 0.5 A/24 V DC)

Article number	6EP1961-2BA21	6EP1961-2BA41	6EP1961-2BA00
Product brand name	SITOP PSE200U	SITOP PSE200U	SITOP select
Type of current supply	Selectivity module, 4 x 10 A Common signal contact	Selectivity module, 4 x 10 A Single- channel signaling	Diagnosis module, 4 x 10 A
Safety			
Galvanic isolation between input and output at switch-off	No	No	No
Operating resource protection class	Class III	Class III	Class III
Certificate of suitability			
CE marking	Yes	Yes	Yes
as approval for USA	UL-Recognized (UL 2367) File E328600; cULus-Listed (UL 508, CSA C22.2 No. 107.1) File E197259	UL-Recognized (UL 2367) File E328600; cULus-Listed (UL 508, CSA C22.2 No. 107.1) File E197259	UL-Recognized (UL 2367) File E328600; cULus-Listed (UL 50 CSA C22.2 No. 107.1) File E19725 cURus (UL 60950, CSA C22.2 No. 60950) File E151273
Standard for safety	according to EN 60950-1 and EN 50178	according to EN 60950-1 and EN 50178	according to EN 60950-1 and EN 50178
Certificate of suitability relating to ATEX	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cULus Class I, Div. 2, Group ABCD, T4		ATEX (EX) II 3G Ex nA nC IIC T4 G cCSAus Class I, Div. 2, Group ABG T4
Shipbuilding approval	DNV GL, ABS	DNV GL, ABS	
Protection class IP	IP20	IP20	IP20
EMC			
Standard			
<ul> <li>for emitted interference</li> </ul>	EN 55022 Class B	EN 55022 Class B	EN 55022 Class B
<ul> <li>for interference immunity</li> </ul>	EN 61000-6-2	EN 61000-6-2	EN 61000-6-2
Operating data			
Ambient temperature			
during operation	-25 +60 °C	-25 +60 °C	0 60 °C
- Note	with natural convection	with natural convection	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C	-40 +85 °C	-40 +85 °C
during storage	-40 +85 °C	-40 +85 °C	-40 +85 °C
Environmental category acc. to IEC 60721	Climate class 3K3, no condensation	Climate class 3K3, no condensation	Climate class 3K3, no condensation
Mechanics			
Type of electrical connection	screw-type terminals	screw-type terminals	screw-type terminals
• at input	+24 V: 2 screw terminals for 0.5 16 mm <sup>2</sup> ; 0 V: 2 screw terminals for 0.5 4 mm <sup>2</sup>	+24 V: 2 screw terminals for 0.5 16 mm <sup>2</sup> ; 0 V: 2 screw terminals for 0.5 4 mm <sup>2</sup>	+24 V: 2 screw terminals for 0.5 16 mm <sup>2</sup> ; 0 V: 2 screw termin for 0.5 4 mm <sup>2</sup>
at output	Output 1 4: 1 screw terminal each for 0.5 4 $mm^2$	Output 1 4: 1 screw terminal each for 0.5 4 $\text{mm}^2$	Output 1 4: 1 screw terminal ea for 0.22 4 mm <sup>2</sup>
<ul> <li>for signaling contact</li> </ul>	3 screw terminals for 0.5 4 mm <sup>2</sup>	1 screw terminal for 0.5 4 mm <sup>2</sup>	2 screw terminals for 0.22 4 mm
<ul> <li>for auxiliary contacts</li> </ul>	Remote reset: 1 screw terminal for 0.5 4 mm <sup>2</sup>	Remote reset: 1 screw terminal for 0.5 4 $mm^2$	-
Width of the enclosure	72 mm	72 mm	72 mm
Height of the enclosure	80 mm	80 mm	90 mm
Depth of the enclosure	72 mm	72 mm	90 mm
Installation width	72 mm	72 mm	72 mm
Mounting height	180 mm	180 mm	190 mm
Net weight	0.2 kg	0.2 kg	0.4 kg
Mounting type	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15	Snaps onto DIN rail EN 60715 35x7.5/15
Product component belonging to	-	-	4x blade-type fuse 15 A
Mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20	-
MTBF at 40 °C	540 979 h	540 979 h	616 675 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)	Specifications at rated input voltag and ambient temperature +25 °C (unless otherwise specified)

ectiv		

Ordering data	Article No.	Accessories	Article No.
SITOP SEL1200	6EP4438-7FB00-3DX0	Device identification labels	3RT2900-1SB20
Selectivity module, 8-channel,		For SITOP SEL1200/1400:	
switching Input: 24 V DC		SIMATIC ET 200SP labels	6ES7193-6LF30-0AW0
Output: 24 V DC/10 A per channel Adjustable response threshold 2 10 A		160 equipment labeling plates, 10 sheets (160 plates)	
SITOP SEL1400	6EP4438-7EB00-3DX0		
Selectivity module, 8-channel, limiting Input: 24 V DC Output: 24 V DC/10 A per channel Adjustable response threshold 2 10 A			
SITOP PSE200U 3 A			
Selectivity module, 4-channel Input: 24 V DC Output: 24 V DC/3 A per channel Adjustable response threshold 0.5 3 A			
<ul> <li>With common alarm signal</li> </ul>	6EP1961-2BA11		
With single-channel signaling	6EP1961-2BA31		
SITOP PSE200U 3 A NEC Class 2			
Selectivity module, 4-channel Input: 24 V DC Output: 24 V DC/3 A per channel Adjustable response threshold 0.5 3 A			
With common alarm signal	6EP1961-2BA51		
With single-channel signaling     SITOP PSE200U 10 A	6EP1961-2BA61	_	
Selectivity module, 4-channel Input: 24 V DC Output: 24 V DC/10 A per channel Adjustable response threshold 3 10 A			
With common alarm signal	6EP1961-2BA21		
With single-channel signaling	6EP1961-2BA41		
SITOP select	6EP1961-2BA00		
Selectivity module, 4-channel Input: 24 V DC Output: 24 V DC/10 A per channel Adjustable response threshold 2 10 A			

### Overview



The SITOP PSE201U buffer module bypasses short-term power failures lasting a few seconds and can be used with all 24 V power supplies of the SITOP smart or SITOP modular product lines. The buffer module is equipped with maintenance-free capacitors and automatically takes over the 24 V power supply in case of a power supply failure.

The SITOP DC UPS modules offer protection in the event of extended power failures. The maintenance-free **DC UPS with capacitors** are able to reliably supply 24 V for several minutes, and the **DC UPS with battery modules** for several hours.

### Benefits

- Bridging of short-term power failures in the time range of seconds
- Totally maintenance-free capacitors as energy storage
- · Short charging times
- Parallel switching of several buffer modules possible
- · Fast mounting onto standard rail and simple wiring


### Application

With short-term power failures, the load current is backed up without interruption via the buffer module in combination with a SITOP smart or SITOP modular 24 V stabilized power supply.

Buffer times:

- 200 ms at 40 A
- 400 ms at 20 A
- 800 ms at 10 A

You can connect up to 8 buffer modules in parallel to extend the buffer time (max. 10 s).



### Design

The buffer module is connected in parallel to the output of the SITOP smart or SITOP modular power supply. The connection to the power supply takes place via only 2 cables.

### Function

### Buffering

In case of a power failure, the buffer module supplies the load current for the 24 V power supply by means of its energy storage units. Maintenance-free capacitors are used as energy storage units.

#### Signaling

The LED on the device signals a supply voltage > 20.5 V.

# Buffer module

# Technical specifications

Article No.	6EP1961-3BA01
	SITOP PSE201U buffer module
Input/Output	Stabilized, isolated DC voltage
Rated voltage Uin rated	24 V DC
Voltage range	24 28.8 V
Control input	-
Rated output voltage Uout rated	<i>U</i> <sub>in</sub> – approx. 1 V
Rated current Iout rated	40 A
Mains buffering	Backup time: • With 40 A load current: 200 ms • With 20 A load current: 400 ms • With 10 A load current: 800 ms • With 5 A load current: 1.6 s
	Reduces the backup time by 100 ms in combination with 6EP1 437-3BA10.
Buffering time, max.	10 s
Protection and monitoring	
Current limiting, static	Тур. 40 А
Short-circuit protection	Electronically
Signaling/alarm signals	
Status display	Green LED for "Supply voltage > 20.5 V"
Signaling	-
Safety	
Galvanic isolation	Yes, SELV acc. to EN 60950-1
Safety class	Class I
Safety test	Yes
CE marking	Yes
UL/cUL (CSA) approval	UL-Listed (UL 508) File E197259, CSA (CSA C22.2 No. 14, CSA C22.2 No. 107.1)
Explosion protection	-
Degree of protection (EN 60529)	IP20
EMC	
Emitted interference	EN 55022 Class B
Noise immunity	EN 61000-6-2
Operating data	
Ambient temperature range	0 +60 °C with natural convection
Transport and storage temperature range	-40 +85°C
Humidity class	Climate class 3K3 according to EN 60721, no condensation
Mechanics	
Connections	One screw-type terminal each for + and - for 0.5 10 mm <sup>2</sup> solid/finely stranded
Dimensions (W x H x D) in mm	70 x 125 x 125
Weight, approx.	1.2 kg
Mounting	Can be snapped onto standard mounting rail EN 60715 35x7.5/15

	6EP1961-3BA01
or SITOP smart and ITOP modular uffer time 100 ms to 10 s ependent on load current	

### Inrush current limiter

### Overview



SITOP inrush current limiters are used to reliably reduce the starting currents that are caused, for example, by transformers or with pulse-controlled power supplies by the rectifier circuit on the input side with capacitor charging.

However, they can also be used as a fuse for relay outputs downstream from the power supply in order to ensure the functionality of these relay modules when high inrush currents are connected to these loads.

### Technical specifications

Article number	6EP4683-6LB00-0AY0	
Product	LOGO! ICL230	
Power supply, type	100-240 V/5 A	
Input	100-240 V/3 A	
Input	1-phase AC	
Rated voltage value V <sub>in rated</sub>	100 240 V	
Voltage range AC	85 264 V	
Wide-range input	Yes	
Built-in incoming fuse	Overload protection in case of error	
Built-in incoming fuse	through non-reversible thermal fuse	
Output		
Output	according to the supply voltage	
Output voltage		
<ul> <li>at AC Rated value</li> </ul>	100 - 240 V AC	
• at AC	85 264	
Product function Output voltage adjustable	No	
Status display	Green LED	
Current range	0 5 A	
Note	Active current limitation for 60 ms to 10 A during switch-on.	
Parallel switching for enhanced performance	No	
Efficiency		
Power loss at V <sub>out rated</sub> , I <sub>out rated</sub> , approx.	1.5 W	
Protection and monitoring		
Short-circuit protection	to be ensured by primary protection element	
type of threshold value setting	Switching frequency max. 2 events per minute. Time-limited increased switching frequency once per hour for one minute (typ. 30 events per minute).	
characteristics of electronic overload switch-off	Non-reversible thermal fuse	
Safety		
Standard for safety	EN 60950-1	
Primary/secondary isolation	No	
Protection class	Class III	
CE mark	Yes	
UL/cUL (CSA) approval		
	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	
Explosion protection		
	No. 107.1), File E197259	
Explosion protection	No. 107.1), File E197259	
Explosion protection FM approval	No. 107.1), File E197259 - -	
Explosion protection FM approval CB approval	No. 107.1), File E197259 - -	
Explosion protection FM approval CB approval Marine approval	No. 107.1), File E197259 - - Yes -	
Explosion protection FM approval CB approval Marine approval Degree of protection (EN 60529)	No. 107.1), File E197259 - - Yes -	
Explosion protection FM approval CB approval Marine approval Degree of protection (EN 60529) EMC	No. 107.1), File E197259 - - Yes - IP20	

### Inrush current limiter

# Technical specifications (continued)


•	,
Article number	6EP4683-6LB00-0AY0
Product	LOGO! ICL230
Power supply, type	100-240 V/5 A
Operating data	
Ambient temperature	
<ul> <li>during operation</li> </ul>	-40 +70 °C
- Note	with natural convection
<ul> <li>during transport</li> </ul>	-40 +85 °C
<ul> <li>during storage</li> </ul>	-40 +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation
Mechanics	
Connection technology	screw-type terminals
Connections	
Supply input	L, N: 1 screw terminal each for 0.5 2.5 mm2 single-core/finely stranded
Output	+, -: 1 screw terminal each for 0.5 2.5 mm <sup>2</sup>
Width of the enclosure	18 mm
Height of the enclosure	90 mm
Depth of the enclosure	53 mm
Required spacing	
• top	20 mm
• bottom	20 mm
• left	0 mm
• right	0 mm
Weight, approx.	0.14 kg
Product feature of the enclosure housing for side-by-side mounting	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15
Other information	Specifications at rated input voltage and ambient temperature +25 $^{\circ}\mathrm{C}$ (unless otherwise specified)

Ordering data	Article No.
SITOP making current limiter	6EP1967-2AA00
Ballast for SITOP power supplies Input: 100 480 V AC, 10 A max Output: 100 480 V AC, 10 A max	
LOGO! ICL230 inrush current limiter	6EP4683-6LB00-0AY0
Ballast for SITOP power supplies Input: 100 240 V AC, 5 A max Output: 100 240 V AC, 5 A max	

© Siemens 2019

# Accessories






10/2 Accessories

### Accessories

### Overview



#### Mounting bracket

The combination of a SITOP power supply and a 90° mounting bracket results in a minimum surface area requirement on the rear panel of the control cabinet (the width of the power supply becomes the depth, and the depth becomes the width). The mounting bracket is suitable for control cabinets with a depth of 320 mm or more.

#### Mounting adapter for standard mounting rail

The 1-phase 24 V/2 A (6ES7305-1BA80-0AA0) and 24 V/5 A (6ES7307-1EA80-0AA0) power supplies are special mechanical versions for SIMATIC S7-300 and can be mounted on S7 rails.

A mounting adapter (6ES7390-6BA00-0AA0) for mounting on the standard mounting rail EN 60715 35x15 is separately available as an accessory.

The 24 V/ 2 A (6ES7307-1BA01-0AA0), 24 V/ 5 A (6ES7307-1EA01-0AA0) and 10 A (6ES7307-1KA02-0AA0) power supplies are variants for SIMATIC S7-300 and can be mounted on S7 rails.

A mounting adapter (6EP1971-1BA00) for installation on DIN rail EN 60715  $35 \times 15/7.5$  is separately available as an accessory.

# Connection plug for devices with degrees of protection IP65 and IP67

For the maintenance-free SITOP UPS500P DC UPS modules (6EP1933-2NC01, 6EP1933-2NC11) in IP65 degree of protection, a connector set (6EP1975-2ES00) for input and output and with a pre-assembled USB cable (2 m long) is available as an accessory.

#### Device labels

20 mm x 7 mm blank device labeling plates with article number 3RT2900-1SB20 (titanium gray) can be used for identification of the power supplies. The package unit comprises 340 labels on frames, 20 labels per frame. For usability, refer to "Accessories" in the technical data of the respective power supplies.

For the product line SITOP PSU6200 as well as SITOP SEL1200/-1400 and SITOP RED1200 the article number 6ES7193-6LF30-0AW0 can be used. The package unit comprises 160 equipment labeling plates, 10 mats (160 labels).

### Technical specifications

#### Mounting bracket 90° for SITOP power Standard 24 V

Mounting bracket	For a depth of 320 mm	
Article number	6EP1971-2BA00	
Dimensions (W x H x D) in mm	100 x 150 x 320	
Sheet thickness	1.5 mm	
Mounting rail, attached	Standard mounting rail EN 60715 35x15	
Weight, approx.	0.9 kg	
Mounting	Can be screwed onto a flat surface (keyhole mounting for hooking onto M6 screws, drill hole distance 90 mr height, 50 mm side)	
Accessories, included	4 M6 combi screws	
Suitable for Power supplies with width 280 mm		

Ordering data	Article No.
SITOP modular signaling module	6EP1961-3BA10
For 6EP1XXX-3BA00 signaling contacts: Output voltage ok, operational availability ok, remote ON/OFF	
SITOP power mounting bracket	
90 degrees, with 35x15 mm stan- dard mounting rail, for power sup- plies with width of up to 280 mm	6EP1971-2BA00
SIMATIC S7-300 mounting adapter	6EP1971-1BA00
For snapping the PS 307 onto stan- dard mounting rail 35x15/7.5 mm suitable for 6ES7307-1BA01*, -1EA01*, -1KA02* and higher	
SIMATIC S7-300 mounting adapter	6ES7390-6BA00-0AA0
for snapping the PS307 onto 35 mm standard rails	
Device identification label 20 mm x 7 mm	
Ti gray	3RT2900-1SB20
Labeling plates SIMATIC ET 200SP	6ES7193-6LF30-0AW0
100 1 11 1 1	

160 equipment labeling plates, 10 mats (160 labels) © Siemens 2019

# Technical information and configuration



- 1/2 Power supplies general
- 1/5 Supply systems data, line-side connection
- 11/8 Possible mains disturbances and their causes
- 1/9 Installation guidelines, mounting areas and fixing options
- 1/10 Parallel connection
- 1/11 Series connection to increase the voltage
- 11/12 Battery charging with SITOP
- 11/13 Fusing of the output circuit 24 V DC, selectivity
- 1/18 Standards and approvals
- 11/19 Certificates

Power supplies general

### Overview

#### **Power supplies**

In plant building or mechanical equipment manufacture, or in any other situations in which electrical controls are used, a safe and reliable power supply is needed to supply the process with power.

The operational reliability of electronic controls and associated reliable operation of automated plants is extremely closely linked to the resistance of the load current supply to failure. Final control elements as well as input and output modules will only respond to command signals if the power supply is operating reliably.

In addition to requirements such as safety, particular demands are placed on the electromagnetic compatibility (EMC) of the power supply with reference to the tolerance range of the output voltage, as well as its ripple.

Important factors that determine problem-free implementation are, in particular:

- · An input current with a low harmonic content
- Low emitted interference
- Adequate immunity (noise immunity) to interference

EMC	Interference phenomena
Emission (emitted interference)	Interference caused by television and radio reception
	Interference coupling on data lines or power supply cables
Noise immunity (immunity to interference)	Faults on the power cable due to switching non-resistive loads such as motors or contactors
	Static discharge due to lightning strikes
	Electrostatic discharge through the human body
	Conducted interference induced by radio frequencies

Selected interference phenomena

#### General notes on DC power supplies

The DC power supply is a static device with one or more inputs and one or more outputs that converts a system of AC voltage and AC current and/or DC voltage and DC current to a system with different DC voltage and DC current values by means of electromagnetic induction for the purpose of transmitting electrical energy.


The type of construction of a DC power supply is primarily decided by its intended use.

### Non-stabilized DC power supplies

The AC mains voltage is transformed using 50 Hz/60 Hz safety transformers to a protective extra-low voltage and smoothed with down-circuit rectification and capacitor filtering.

In the case of non-stabilized DC power supplies, the DC output voltage is not stabilized at a specific value, but the value is varied in accordance with the variation in (mains) input voltage and the loading.

The ripple is in the Volt range and is dependent on the loading. The value for the ripple is usually specified as a percentage of the DC output voltage level. Non-stabilized DC power supplies are characterized by their rugged, uncomplicated design that is limited to the important factors and focused on a long service life.





Stabilized DC power supplies

Stabilized DC power supplies have electronic control circuits that maintain the DC voltage at the output at a specific value with as little variation as possible. Effects such as variation in input voltage or changes in load at the output are electrically compensated in the specified function area.

The ripple in the output voltage for stabilized DC power supplies lies in the millivolt range and is mainly dependent on the loading at the outputs.


Stabilized DC power supplies can be implemented on different functional principles. The most common types of circuit are:

- · Linear stabilized power supplies
- Magnetic voltage stabilizers
- · Secondary pulsed switched-mode power supplies
- · Primary pulsed switched-mode power supplies

The most suitable principle for a particular application case will depend mainly on the application. The objective is to generate a DC voltage to supply the specific load as inexpensively and as accurately as possible.

### Overview (continued)

Power supplies with in-phase regulation



Block diagram: Transformer with in-phase regulation

The transformer with in-phase regulation operates according to a conventional principle. The supply is provided from an AC supply system (one, two or three conductor supply).

A transformer is used to adapt it to the required secondary voltage.

The rectified and filtered secondary voltage is converted to a stabilized voltage at the output in a regulation section. The regulation section comprises a final control element and a control amplifier. The difference between the stabilized output voltage and the non-stabiliYzed voltage at the filter capacitor is converted into a thermal loss in the final control element. The final control element functions in this case like a rapidly changeable ohmic impedance. The thermal loss that arises in each case is the product of output current and voltage drop over the final control element.

This system is extremely adaptable. Even without further modifications, several output voltages are possible. In the case of multiple outputs, the individual secondary circuits are usually generated from separate secondary windings of the input transformer. Some applications can only be resolved in accordance with this circuit principle. Especially when highly accurate regulation, minimal residual ripple and fast compensation times are required.

The efficiency is, however, poor and the weight and volume are considerable. The transformer with in-phase regulation is therefore only an economical alternative at low power ratings.


#### Advantages:

- Simple, well-proven circuit principle
- Good to excellent control characteristics
- Fast compensation time

#### Disadvantages:

- Relatively high weight and large construction volume due to the 50 Hz transformer
- Poor efficiency, heat dissipation problems
- · Low storage time

#### Magnetic stabilizer



Block diagram: Magnetic stabilizer

The complete transformer comprises two components. The "ferro resonator" and a series-connected auxiliary regulator. The input winding and the resonance winding of the magnetic stabilizer are decoupled to a large extent by means of the air gap. The magnetic stabilizer supplies a well-stabilized AC voltage. This is rectified and filtered. The transformer itself is operated in the saturation range.

The ferro resonator frequently has a transformer with in-phase regulation connected downstream to improve the control accuracy. Secondary pulsed switched-mode regulators are frequently also connected downstream.

The magnetic stabilizer technique is reliable and rugged but is also large-volume, heavy and relatively expensive.


#### Advantages:

- Good to excellent control characteristics in combination with transformer with in-phase regulation connected downstream
- Significantly better efficiency than a transformer with in-phase regulation alone

Disadvantages:

- · The ferro resonator is frequency dependent
- The power supplies are large and heavy due to the magnetic components

### Secondary pulsed switched-mode power supplies:



Block diagram: Secondary pulsed switched-mode power supplies

Isolation from the supply system is implemented in this case with a 50 Hz transformer. Following rectification and filtering, the energy is switched at the output by means of pulsing through a switching transistor in the filtering and storage circuit. Thanks to the transformer at the input that acts as an excellent filter, the mains pollution is low.

The efficiency of this circuit is extremely high.

This concept offers many advantages for power supplies with numerous different output voltages.

To protect the connected loads, however, care must be taken; in the event of the switching transistor breaking down, the full, non-stabilized DC voltage of the filter capacitor will be applied to the output. However, this danger also exists in the case of linear stabilized power supplies.

### Advantages:

- · Simple design and high efficiency
- Multiple outputs, also galvanically isolated from one another, are easily implemented by means of several secondary windings
- Fewer problems with interference than with primary pulsed switched-mode power supplies

#### Disadvantages:

- The 50 Hz transformer makes the power supplies relatively large and heavy
- The output ripple (spikes) correspond to those of a primary pulsed switched-mode power supply


11

### Power supplies general

### **Overview** (continued)

#### Primary pulsed switched-mode power supplies:

The term SMPS (Switch Mode Power Supply) or primary switched-mode regulator is often used in the literature.



Block diagram: Single-ended forward converter

The primary switched-mode regulators are available in many different circuit versions. The most important basic circuits are single-ended forward converters, flyback converters, halfbridge converters, full-bridge converters, push-pull converters and resonance converters.

The general principle of operation of the primary switched-mode regulator is shown in the block diagram of the single-ended forward converter:

The non-stabilized supply voltage is first rectified and filtered. The capacitance of the capacitor in the DC link determines the storage time of the power supply on failure of the input voltage. The voltage at the DC link is approximately 320 V DC for a 230 V supply. A single-ended converter is then supplied with this DC voltage and transfers the primary energy through a transformer to the secondary side with the help of a pulse width regulator at a high switching frequency. The switching transistor has low power losses when functioning as a switch so that the power balance lies between > 70% and at least 90%, depending on the output voltage and current.

The volume of the transformer is small in comparison with a 50 Hz transformer due to the high switching frequency because the transformer size, taking into account the higher switching frequency, is smaller. Using modern semiconductors, clock frequencies of 100 kHz and above can be achieved. However, switching losses increase at excessively high clock frequencies so that in each case a compromise has to be made between high efficiency and the largest possible clock frequency. In most applications, the switching frequencies lie between approximately 20 kHz and 250 kHz depending on the output power.

The voltage from the secondary winding is rectified and filtered. The system deviation at the output is fed back to the primary circuit through an optocoupler. By controlling the pulse width (conducting phase of the switching transistor in the primary circuit), the necessary energy is transferred to the secondary circuit and the output voltage is regulated. During the non-conducting phase of the switching transistor, the transformer is demagnetized through an auxiliary winding. Exactly the same amount of energy is transferred as is removed at the output. The maximum pulse width for the pulse duty factor for these circuits is < 50%.

### Advantages:

- Small magnetic components (transformer, storage reactor, filter) thanks to the high operating frequency
- · High efficiency thanks to pulse width regulation
- Compact equipment units
- Forced-air cooling is not necessary up to the kW range
- High storage times are possible in case of power failure by increasing the capacitance in the DC link
- Large input voltage range possible

### Disadvantages:

- · High circuit costs, many active components
- · High costs for interference suppression
- The mechanical design must be in accordance with HF criteria

Primary switched-mode power supplies have taken over from the other switching modes in recent years. This is due, in particular, to their compact size, minimal weight, high efficiency and excellent price/performance ratio.

### Summary

The most important characteristics of the circuit types described above are summarized in the table.

Comparison criteria	Connection methods			
	Primary- switched mode	Secondary- switched mode	Transformer with in-phase regulation	Magnetic stabilizer
Input voltage range	Very large	Average	Very small	Large
Regulation speed	Average	Average	Very fast	Slow
Storage time after power failure	Very long	Long	Very short	Long
Residual ripple	Average	Average	Very low	Average
Power loss	Very small	Small	Large	Very small
Size	Very small	Average	Very large	Large
Weight	Very light	Average	Heavy	Very heavy
Interference suppression overhead	Very large	Average	Low	Average

Comparison criteria for basic circuit versions

Supply systems data, line-side connection

### Overview

### Network data

When dimensioning and selecting plant components, the supply systems data, supply system conditions and operating modes must be taken into account for these components.

The most important data for a supply system include the rated voltage and rated frequency. These data for the supply system are designated as rated values in accordance with international agreements.

#### Generally used rated voltages and rated frequencies

In Europe the EN 60038 standard "CENELEC standard voltages" applies.

This standard includes most of the international standard IEC 60038, 7. Edition, 2009, "IEC standard voltages".

The IEC 60038 standard is the result of an international agreement to reduce the diverse rated voltage values that are in use for electrical supply networks and traction power supplies, load installations and equipment.

As concerns the low-voltage range, note that in the EN 60038 the 220 V/380 V values (previously applicable in continental Europe) and 240 V/415 V values (previously applicable in the United Kingdom) for three-phase networks have been replaced by a single standardized value of 230 V/400 V. The supply frequency in Europe is 50 Hz.

The tolerances for the rated voltages of the supply systems that were specified for the transition period up to 2003 were intended to ensure that equipment rated for the existing voltages could be operated safely until the end of its service life.

Year	Rated voltage	Tolerance range
Up to 1987	220 V/380 V	-10% to +10%
1988 to 2003	230 V/400 V	-10% to + 6%
Since 2003	230 V/400 V	-10% to +10%

Conversion of low-voltage systems

Supply voltages over 400 V (e.g. 500 V, 690 V) are occasionally used in Europe in large industrial plants.

The IEC recommendation of 230 V/400 V has been implemented as national regulation in the most important countries, as far as the conditions in these countries allow.

In North America, Central America and some northern South American countries the rated value for AC supply voltage is 120 V; but twice the supply voltage, i.e. 240 V, is common for larger loads. The low-voltage supply systems are normally implemented in these countries as single-phase three-conductor systems. Three-phase AC current is often unavailable to small consumers, if it exists at all, so the voltage is 208 V or 415 V. Three-phase networks are available for larger consumers at 480 V. The supply frequency is 60 Hz.

In Asia, AC supply voltages of 100 V or 110 V (50 Hz or 60 Hz) are also common.

Worldwide, numerous country-specific and regional characteristics prevail about which the local plant operators must be directly consulted.

International	supply	voltages	and	frequencie	es
in low-voltag	e syste	ms			

Country	Line voltage
Western Europe:	
Belgium	50 Hz 230/400 – 127-220 V
Denmark	50 Hz 230/400 V
Germany	50 Hz 230/400 V
Finland	50 Hz 230/400-500 <sup>1)</sup> – 660 <sup>1)</sup> V
France	50 Hz 127/220 – 230/400 – 500 <sup>1)</sup> – 380/660 <sup>1)</sup> – 525/910 <sup>1)</sup> V
Greece	50 Hz 230/400 – 127/220 <sup>2)</sup> V
Great Britain	50 Hz 230/400 V
Ireland	50 Hz 230/400 V
Iceland	50 Hz 127/220 <sup>2)</sup> – 230/400 V
Italy	50 Hz 127/220 – 230/400 V
Luxembourg	50 Hz 230/400 V
The Netherlands	50 Hz 230/400 – 660 <sup>1)</sup> V
Northern Ireland	50 Hz 230/400 – Belfast 220/380 V
Norway	50 Hz 230-230/400-500 <sup>1)</sup> – 690 <sup>1)</sup> V
Austria	50 Hz 230/400 – 500 <sup>1)</sup> – 690 <sup>1)</sup> V
Portugal	50 Hz 230/400 V
Sweden	50 Hz 230/400 V
Switzerland	50 Hz 230/400 – 500 <sup>2)</sup> V
Spain	50 Hz 230/400 V
Eastern Europe:	
Albania	50 Hz 230/400 V
Bulgaria	50 Hz 230/400 V
Russian Federation	50 Hz 230/400 - 690 <sup>1)</sup> V
Croatia	50 Hz 230/400 V
Poland	50 Hz 230/400 V
Romania	50 Hz 230/400 V
Serbia	50 Hz 230/400 V
Slovakia	50 Hz 230/400 - 500 <sup>1)</sup> - 690 <sup>1)</sup> V
Slovenia	50 Hz 230/400 V
Czech Republic	50 Hz 230/400 - 500 <sup>1)</sup> - 690 <sup>1)</sup> V
Hungary	50 Hz 230/400 V

1) Industry only

2) No further expansion

# Supply systems data, line-side connection

### **Overview** (continued)

Country	Line voltage		
Middle East:			
Afghanistan	50 Hz 220/380 V		
Bahrain	50 Hz 230/400 V		
Cyprus	50 Hz 240/415 V		
Iraq	50 Hz 220/380 V		
Israel	50 Hz 230/400 V		
Jordan	50 Hz 220/380 V		
Kuwait	50 Hz 240/415 V		
Lebanon	50 Hz 110/190 – 220/380 V		
Oman	50 Hz 220/380 – 240/415 V		
Qatar	50 Hz 240/415 V		
Saudi Arabia	60 Hz 127/220 - 220/380 - 480 <sup>1)</sup> V (220/380 - 240/415 V 50 Hz: a few remaining areas only)		
Syria	50 Hz 115/200 - 220-380 - 400 <sup>1)</sup> V		
Turkey	50 Hz 220/380 V (parts of Istanbul: 110/190 V)		
United Arab Emirates (Abu Dhabi; Ajman; Dubai; Fujairah; Ras al Khaymah; Sharjah; Um al Qay- wayn)	50 Hz 220/380 – 240/415 V		
Yemen (North)	50 Hz 220/380 V		
Yemen (South)	50 Hz 230/400 V		
Far East:			
Bangladesh	50 Hz 230/400 V		
Burma	50 Hz 230/400 V		
People's Republic of China	50 Hz 127/220 – 220/380 V (in mining: 1140 V)		
Hong Kong	50 Hz 200/346 V		
India	50 Hz 220/380 - 230/400 - 240/415 V		
Indonesia	50 Hz 127/220 - 220/380 - 400 <sup>1)</sup> V		
Japan	50 Hz 100/200 – 400 <sup>1)</sup> V		
South Honshu, Shikoku, Kyushu, Hokkaido, North Honshu	60 Hz 110/220 – 440 <sup>1)</sup> V		
Cambodia	50 Hz 120/208 V – Phnom Penh 220/238 V		
Korea (North)	60 Hz 220/380 V		
Korea (South)	60 Hz 100/200 <sup>2)</sup> – 220/380 – 440 <sup>1)</sup> V		
Malaysia	50 Hz 240/415 V		
People's Republic of Mongolia	50 Hz 220/380 V		
Pakistan	50 Hz 230/400 V		
Philippines	60 Hz 110/220 – 440 V		
Singapore	50 Hz 240/415 V		
Sri Lanka	50 Hz 230/400 V		
Taiwan	60 Hz 110/220 – 220 – 440 V		
Thailand	50 Hz 220/380 V		
Vietnam	50 Hz 220/380 V		

Country	Line voltage
North America:	
Canada	60 Hz 600 – 120/240 – 460 – 575 V
USA	
	60 Hz 120/208 – 120/240 – 277/480 – 600 <sup>1)</sup> V
Central America:	
Bahamas	60 Hz 115/200 – 120/208 V
Barbados	50 Hz 110/190 – 120/208 V
Belize	60 Hz 110/220 – 220/440 V
Costa Rica	60 Hz 120/208 <sup>2)</sup> – 120/240 – 127/220 – 254/440 <sup>2)</sup> – 227/480 <sup>1)</sup> V
Dominican Republic	60 Hz 120/208 – 120/240 – 480 <sup>1)</sup> V
Guatemala	60 Hz 120/208 – 120/240 – 127/220 – 277/480 <sup>1)</sup> – 480 <sup>1)</sup> – 550 <sup>1)</sup> V
Haiti	50 Hz 220/380 V (Jacmel), 60 Hz 110/220 V
Honduras	60 Hz 110/220 - 127/220 - 277/480 V
Jamaica	50 Hz 110/220 – 440 <sup>1)</sup> V
Cuba	60 Hz 120/240 - 220/380 - 277/480 <sup>1)</sup> - 440 <sup>1)</sup> V
Mexico	60 Hz 127/220 – 440 <sup>1)</sup> V
Nicaragua	60 Hz 110/220 – 120/240 – 127/220 – 220/440 – 254/40 <sup>1)</sup> V
Panama	60 Hz 120/208 <sup>1)</sup> – 120/240 – 254/4401 – 277/480 <sup>1)</sup> V
Puerto Rico	60 Hz 120/208 – 480 V
El Salvador	60 Hz 110/220 – 120/208 – 127/220 – 220/440 – 240/480 <sup>1)</sup> – 254/440 <sup>1)</sup> V
Trinidad	60 Hz 110/220 - 120/240 - 230/400 V
South America:	
Argentina	50 Hz 220/380 V
Bolivia	60 Hz 220/380 – 480 V, 50 Hz 110/220 – 220/380 V (exception)
Brazil	60 Hz 110/220 – 220/440 – 127/220 – 220/380 V
Chile	50 Hz 220/380 V
Ecuador	60 Hz 120/208 – 127/220 V
Guyana	50 Hz 110/220 V (Georgetown), 60 Hz 110/220 – 240/480 V
Columbia	60 Hz 110/220 - 150/260 - 440 V
Paraguay	60 Hz 220/380 – 220/440 V
Peru	60 Hz 220 – 220/380/440 V
Surinam	60 Hz 115/230 – 127/220 V
Uruguay	50 Hz 220 V
Venezuela	60 Hz 120/208 - 120/240 - 208/416 - 240/480 V

Industry only
 No further expansion

#### Supply systems data, line-side connection

Overview (c	continued)
-------------	------------

Country	Line voltage
Africa:	
Egypt	50 Hz 110/220 – 220/380 V
Ethiopia	50 Hz 220/380 V
Algeria	50 Hz 127/220 – 220/380 V
Angola	50 Hz 220/380 V
Benin	50 Hz 220/380 V
Ivory Coast	50 Hz 220/380 V
Gabon	50 Hz 220/380 V
Ghana	50 Hz 127/220 – 220/380 V
Guinea	50 Hz 220/380 V
Kenya	50 Hz 220/380 V
Cameroon	50 Hz 127/220 – 220/380 V
Congo	50 Hz 220/380 V
Liberia	60 Hz 120/208 – 120/240 V
Libya	50 Hz 127/220 <sup>2)</sup> – 220/380 V
Madagascar	50 Hz 127/220 – 220/380 V
Malawi	50 Hz 220/380 V
Mali	50 Hz 220/380 V
Morocco	50 Hz 115/200 – 127/220 – 220/380 – 500 <sup>1)</sup> V
Mauritius	50 Hz 240/415 V
Mozambique	50 Hz 220/380 V
Namibia	50 Hz 220/380 V
Niger	50 Hz 220/380 V
Nigeria	50 Hz 220/415 V
Rwanda	50 Hz 220/380 V
Zambia	50 Hz 220/380 V - 415 - 550 <sup>1)</sup> V
Senegal	50 Hz 127/220 – 220/380 V
Sierra Leone	50 Hz 220/380 V
Somalia	50 Hz 220-220/440 V
Sudan	50 Hz 240/415 V
South Africa	50 Hz 220/380 - 500 <sup>1)</sup> - 550/950 <sup>1)</sup> V
Swaziland	50 Hz 220/380 V
Tanzania	50 Hz 230/400 V
Тодо	50 Hz 127/220 – 220/380 V
Tunisia	50 Hz 115/200 – 220/380 V
Uganda	50 Hz 240/415 V
Zaire	50 Hz 220/380 V
Zimbabwe	50 Hz 220/380 V

<sup>1)</sup> Industry only

<sup>2)</sup> No further expansion

#### Connection and fusing on the line side

All SITOP and LOGO!Power supplies are built-in devices. Compliance with the pertinent country-specific regulations is essential for installation and electrical connection of the devices. During installation, protective gear and isolating gear must be provided for activating the power supply.

Power supply units cause a current inrush immediately after connection of the input voltage due to charging of the load capacitor, however, it falls back to the rated input current level after a few milliseconds. Aside from the internal impedances of the power supply, the inrush current is dependent on the size of the input voltage applied as well as the source impedance of the supply network and the line impedance of the supply line. The maximum inrush current for the power supplies is specified in the applicable technical data. It is important for dimensioning upstream protective devices.

Single-phase SITOP and LOGO!Power supplies are equipped with internal device protection (fuses). For connection to the supply system, only one protective device (fuse or MCB) must be provided for line protection in accordance with the rated current of the installed cable. The circuit-breakers recommended in the data sheets and operating instructions have been selected such that even during the maximum current inrush that can occur under worst-case conditions on switching on the supply voltage, the circuit-breaker will not trip. A two-pole connected miniature circuit-breaker is required for the connection of certain device types.

Three-phase SITOP power supplies do not have internal device protection. The up-circuit protective device (3-phase coupled miniature circuit breaker or motor protection switch) protects the cables and devices. The protective devices specified in the data sheets and operating instructions are optimized to the characteristics of the relevant power supplies.

11

#### Possible mains disturbances and their causes

### Overview

The quality of the mains voltage has become a decisive factor in the functioning, reliability, maintenance costs and service life of highly sensitive electronic installations and devices (computers, industrial controls, instrumentation, etc.).

Mains disturbances cause system failures and affect the function of plants as well as electronic loads. They can also result in total failure of the installation or equipment.

The most frequent types of disturbance are:

- Long-term overvoltages
- Long-term undervoltages
- Interference pulses and transients
- · Voltage dips and surges
- Electrical noise
- Momentary network failure
- Long-term network failure

Mains disturbances can be caused by a number of things, e.g.:

- Switching operations in the supply system
- Long cable paths in the supply system
- Environmental influences such as thunderstorms
- Mains overloads

Typical causes of mains disturbances generated in-house are:

- Thyristor-controlled drives
- · Elevators, air-conditioning, photocopiers
- · Motors, reactive-power compensation systems
- · Electrical welding, large machines
- Switching of lighting equipment

Disturbances in mains voltages can occur individually or in combination. Possible reasons for these disturbances, their effects and countermeasures can include:

System disturbances	Percentage of total disturbance	Result	Measure
Overvoltage The supply voltage is exceeded by more than +6% for a prolonged period (acc. to IEC 60038)	Approx. 15% - 20%	Can result in overheating and even thermal destruction of individual components. Causes total failure.	SITOP power supplies with their wide operating voltage range offer sufficient protection against minor network over- voltages outside the permissible toler- ance
Line undervoltage The supply voltage is undershot by more than –10% for a prolonged period (acc. to DIN IEC 60038)	Approx. 20% - 30%	Can result in undefined operating states of loads. Causes data errors.	Use of a SITOP DC-UPS (uninterrupt- ible DC power supply) see Section 11
Interference pulses Energy-rich pulses (e.g. 700 V/1 ms) and energy- poor transients (e.g. 2500 V/20 µs) result from switching operations in the supply system	Approx. 30% - 35%	Can result in undefined operating states of the loads and can lead to the destruction of components.	Use of surge protectors, see Catalog LV 10.1 2013, Section 6
Voltage dips and surges The voltage level changes suddenly and in an uncontrolled manner, e.g. due to changes in loading and long cable routes	Approx. 15% - 30%	Can result in undefined operating states and destruction of components. Cause data errors.	Thanks to their internal buffer time, SITOP power supplies offer sufficient protection against short power failures
Electrical noise A mix of frequencies superimposed on the mains due to bad grounding and/or strong HF emitters such as radio transmitters or thunderstorms	Approx. 20% - 35%	Can result in undefined operating states of loads. Causes data errors.	Due to internal switching measures, SITOP power supplies offer sufficient immunity to electromagnetic interfer- ence
voltage interruption Short-term interruption of the supply voltage (up to approx. 100 ms) due to short-circuiting in neighboring supply systems or starting of large electrical machines.	Approx. 8% - 10%	Can result in undefined operating states of loads, especially those with insufficient mains buffering. Causes data errors.	Use of a SITOP buffer module (in connection with SITOP smart or SITOP modular) see Section 10
Voltage interruption Long interruption of the supply voltage (longer than approx. 100 ms)	Approx. 2% - 5%	Can result in undefined operating states of loads, especially those with insufficient mains buffering. Causes data errors.	Use of a SITOP DC-UPS (uninterruptible DC power supply) see Section 11

Installation guidelines, mounting areas and fixing options

### Overview

### Installation guidelines

SITOP und LOGO!Power power supplies are mostly built-in devices. They must be mounted vertically so that the supply air can enter the ventilation slots at the bottom of the devices and leave through the upper part of the devices. The minimum clearances specified in the relevant product documentation (operating instructions, device manuals) for the top and bottom of the devices must be observed to ensure free air convection. Side clearance is not required.

The option of mounting on standard mounting rails, wall mounting or mounting in non-vertical positions with the appropriate derating is specified in the respective device manuals.

### Everything for project planning

Comprehensive information is available for mechanical and electrical engineering, for example, 3D data, circuit diagram macros, device manuals, product data sheets and certificates. The information is available for download via the CAx Download Manager.

Further information is available on the Internet at

http://www.siemens.com/cax

### **Parallel connection**


### Overview

#### Parallel connection for redundant operation

Two SITOP power supplies of the same type can be connected in parallel through diodes for a redundant configuration. 100% redundancy only exists for two power supplies when the total load current is no higher than that which one power supply can supply alone and when the supply for the primary side is also implemented redundantly (i.e. a short-circuit on the primary side will not trigger a shared fuse which would disconnect both power supplies from the mains).

Parallel connection with decoupling diodes for redundant operation is permitted for all SITOP power supplies. The diodes V1 and V2 are used for decoupling. They must have a blocking voltage of at least 40 V (when decoupling from 24 V power supplies) and it must be possible to load them with a current equal to or greater than the maximum output current of the respective SITOP power supply. For diode dimensioning, see the following note "General information on selection of diodes".

The ready-to-use add-on "SITOP PSE202U modular redundancy modules" are available as a simple alternative to diode dimensioning (Article number: 6EP1962-2BA00, 6EP1964-2BA00, 6EP1961-3BA21) for redundant connection of two power supplies.



Parallel connection of two SITOP power supplies for redundant operation

#### General information on selection of diodes:

The diodes must be dimensioned for the maximum dynamic current. This can be the dynamic current during power-up in the short-circuit case, or the dynamic current during a short-circuit in operation (the larger of the two values should be taken from the relevant technical specifications).

To dissipate the significant power loss of the decoupling diodes (sustained short-circuit current x diode conductive-state volt-age), the diodes must be equipped with suitably dimensioned heat sinks.

An additional safety margin is recommended, because the output capacitor integral to the power supply generates an additional peak current in the short-circuit case. This additional current flows only for a few milliseconds so it is within the period in which diodes are permitted to be loaded with a multiple of the rated current (8.3 ms, known as the permissible surge current for diodes).

#### Example

Two 1-phase SITOP modular power supplies with 10 A rated output current (Article number: 6EP1334-3BA10) are connected in parallel. The dynamic current in the event of a short-circuit during operation is approx. 30 A for 25 ms.

The diodes should therefore have a loading capability of 40 A to be safe, the common heat sink for both diodes must be dimensioned for the maximum possible current of approximately 24 A (sustained short-circuit current) x diode conductive-state voltage.

#### Parallel connection for performance enhancement

To enhance performance, identical types of most SITOP power supplies can be connected in parallel galvanically (the same principle as parallel connection for redundant operation, but without decoupling diodes):

The types permitted for direct galvanic parallel connection are listed in the relevant technical specifications under "Output, parallel connection for performance enhancement".

#### Requirement:

- The output cables connected to terminals "+" and "-" of every power supply should be installed with an identical length and cross-section (or the same impedance) to the common external linking point.
- The power supplies connected in parallel must be switched simultaneously using a common switch in the mains supply line (e.g. using the main switch available in control cabinets).
- The output voltages of the power supplies must be measured under no-load operation before they are connected in parallel and are permitted to differ by up to 50 mV. This usually corresponds to the factory default setting. If the output voltage is changed in case of variable power supplies, the "-" terminals should first be connected and then the voltage difference between the "+" output terminals measured under no-load conditions before they are connected. The voltage difference must not exceed 50 mV.

### Note


With a direct galvanic connection in parallel of more than two SITOP power supplies, further circuit measures may be necessary for short-circuit and overload protection!

#### Overview

#### Series connection to increase the voltage

To generate a load voltage of e.g. 48 V DC, two 24 V SITOP power supplies of the same type can be connected in series. The SITOP outputs "+" and "-" are isolated up to at least 60 V DC against PE (creepages and clearances as well as radio interference suppression capacitors on "+" and "-" against PE), so that with this type of series connection (see Figure), the following points can be grounded:

- "-" of the lower power supply (results in +48 V DC against PE)
- Midway "+"/ "-" between both power supplies (results in ±24 V DC against PE)
- "+" of the upper power supply (results in -48 V DC against PE)



Series connection of two SITOP power units to double the voltage

#### Note:

If two devices are connected in parallel, it cannot be guaranteed that the voltage will remain below the maximum permissible SELV voltage of 60 V DC in the event of a fault.

The purpose of diodes V1 and V2 is to protect the electrolytic output capacitor integrated in the power supply against reverse voltages > 1 V. As a result of the not absolutely simultaneous power-up (even when a common mains switch is used for switching on, differences of a few tens of milliseconds can occur between the various startup-up delays), the power supply which starts up more quickly supplies current from output "--" of the slower power supply whose output electrolytic capacitor is then theoretically impermissibly discharged.

The internal LC filter causes the internal rectifier diode on the secondary side of the slower-starting power supply to accept this current a few milliseconds later; this means that the external diode connected with its anode to "-" and cathode to "+" is essential on each power supply. These diodes are, however, only loaded dynamically so that the 8.3 ms surge current loading capability (specified in the data sheets for suitable diodes) can be used as a basis for dimensioning and it is not usually necessary to cool the diodes using heat sinks.

#### Example:

Two 1-phase SITOP power supplies with 10 A rated output current (Article number: 6EP1334-1AL12) should be connected in series to increase the voltage. They supply approximately 35 A dynamically for 700 ms on power-up in the short-circuit case or also, for example, with loads with a high-capacity input capacitor that momentarily act as a short-circuit at the start.

Suitable diodes for V1 and V2 are, for example, of Type SB 340<sup>1)</sup> (Schottky diode in axially wired enclosure DO-201AD with approximately 5.3 mm diameter and approximately 9.5 mm length of body).

40 V are permissible as the blocking voltage, and the stationary direct current load capacity  $I_{\rm FAV}$  is 3 A. The dynamic surge current loading capacity  $I_{\rm FSM}$  important in this case is sufficient for the selected SITOP power supply at more than 100 A for 8.3 ms. For SITOP power supplies with a lower rated output current, this diode can also be used, but it is over-dimensioned.

<sup>1)</sup> We do not accept any liability for this diode recommendation.

#### **Battery charging with SITOP**

#### Overview

#### Battery charging with SITOP power supplies

The SITOP PSU3800 12 V/20 A

(Article No. 6EP3424-8UB00-0AY0), 24 V/17 A

(Article No. 6EP3436-8UB99-0AY0) and 24 V/40 A (Article No. 6EP3437-8UB00-0AY0) power supplies are suitable for charging lead rechargeable batteries. For a U-I characteristic curve set to parallel operation, the battery to be charged is charged with a constant current until approximately 95% of the set SITOP output voltage is reached. The charging current is then continuously reduced from 1.2 x rated current at 95% of the set voltage to approximately 0 A or the self-discharge current of the battery at 100% of the set output voltage, i.e. the resistance characteristic in this range.

As reverse voltage and reverse polarity protection, we recommend that a diode suitable for at least 1.2 x the rated current of the power supply with a blocking voltage of at least 40 V is connected in series with the "+" output (anode connected to "+" output of the SITOP PSU3800 and cathode connected to positive pole of the battery).

The output voltage of the power supply must be set at no-load to the end-of-charging voltage plus the voltage drop at the diode. For an end-of-charging voltage of e.g. 27.0 V DC (usual at 20 °C to 30 °C battery temperature; specifications of the battery manufacturer must be observed!) and 0.8 V voltage drop at the diode, the power supply must be set to 27.8 V during no-load operation.

# General note for using SITOP power supplies as a battery-charging unit

When using SITOP as a battery charging unit, VDE 0510 or relevant national regulations must be observed, and adequate ventilation of the battery location provided. SITOP power supplies are designed as built-in units, and touch protection should therefore be provided by installation in an appropriate housing.

The value recommended by the battery manufacturer must be set as the end-of-charge voltage (depending on the battery temperature). An ideal temperature for the lead-acid battery is between +20 °C to +30 °C and the recommended end-of-charge voltage in this case is usually about 27 V.

#### Fusing of the output circuit 24 V DC, selectivity

#### Overview

### Fusing of 24 V power supply circuits and selectivity

With non-stabilized rectifiers (power transformer equipped with rectifier) the output usually had to be protected with a suitable fuse so that its rectifier diodes would not fail in the event of an overload or a short-circuit (this would destroy the DC loads due to the resulting alternating voltage and lead to serious damage in most cases).

On the other hand, the stabilized SITOP power supplies are provided with integral electronic short-circuit protection that automatically protects both the power supply and the supplied 24 V DC circuits against an excess current in the event of an overload/short-circuit. A distinction must be made between the following three cases with respect to fusing on the secondary side:

#### **Example 1: No fusing**

Fusing the secondary side (24 V DC) for protecting the load circuits and lines is not required if the respective cross-sections are selected for the maximum possible output current RMS value. Depending on the event (short-circuit or overload) this may either be the short-circuit RMS value or the current limitation value.

Example SITOP modular 10 (Article No.: 6EP1334-3BA10)

- 10 A rated current
- Current limitation typ. 12 A
- Short-circuit current rms value approximately 12 A

The technical specifications usually specify typical values, maximum values are approximately 2 A above the typical value. In the example here, a maximum possible output current rms value of approximately 14 A must therefore be used for line dimensioning.

#### **Example 2: Reduced conductor cross-sections**

If smaller conductor cross-sections are used than are specified in the relevant standards (e.g. EN 60204-1), the affected 24 V load infeed cables must be protected with a suitable line protection.

It is then unimportant whether the power supply enters current limiting mode (overload) or delivers the maximum short-circuit current (low-resistance short-circuit). The load supply is in any case protected against an overload by the line protection matched to the conductor cross-section.

#### **Example 3: Selectivity**

In cases where a load which has failed (e.g. because of a shortcircuit) has to be rapidly detected or where it is essential to selectively switch it off before the power supply enters current limiting mode (with current limiting mode, the voltage would also fall for all remaining 24 V DC loads), there are two possibilities for the secondary side connection:

- Use of a SITOP PSE200U selectivity module or the SITOP select diagnostics module for distributing the 24 V DC supply among up to 4 load feeders.
   Each output can be set between 0.5 A and 3 A (Article No.: 6EP1961-2BA11, -2BA31, -2BA51, -2BA61) or 3 A and 10 A (Article No.: 6EP1961-2BA21, -2BA41) or 2 A and 10 A (Article No.: 6EP1961-2BA00).
- Series connection of appropriate 24 V DC fuses or miniature circuit breakers

The basis for selection of the 24 V DC fuse or miniature circuit breaker is the short-circuit current above the rated current which the SITOP power supplies deliver in the event of a short-circuit during operation (values are specified in the respective technical specifications under "Output, dynamic V/I on short-circuit during operation").

It is not easy to calculate the amount of the short-circuit current flowing into the usually not ideal "short-circuit" and the amount flowing into the remaining loads. This depends on the type of overload (high-resistance or low-resistance short-circuit) and the type of load connected (resistive, inductive and capacitive/ electronic loads).

However, it can be assumed with a first approximation in the average case encountered in practice that the difference of dynamic overcurrent minus 50 % SITOP rated output current is available for the immediate tripping of a circuit breaker within a typical time of 12 ms (with 14 times the rated DC with a circuit breaker characteristic C acc. to IEC 60898, or with 7 times the rated DC with a circuit breaker characteristic A). Please refer to the following tables for circuit-breakers appropriate for selected fusing according to this assumption.

# Fusing of the output circuit 24 V DC, selectivity

### **Overview** (continued)

List of ordering data and tripping characteristics of single-pole circuit-breakers 5SY4...

acc. to IEC 60898 / EN 60898, for use up to 60 V DC (250 V AC, switching capacity 10000 A)

Rated current	Tripping characteristic	Article No.	Range for immediate tripping < 100 ms for operation with direct current (alternating current)	Required DC for immediate tripping in < 100 ms	Required DC for immediate tripping in approx. 12 ms
1 A	Туре А	5SY4 101-5	DC: 2 5 (AC: 2 3) x / <sub>Rated</sub>	2 5 A DC	5 A DC
1 A	Туре С	5SY4 101-7	DC: 5 14 (AC: 5 10) x / <sub>Rated</sub>	5 14 A DC	14 A DC
1.6 A	Туре А	5SY4 115-5	DC: 2 5 (AC: 2 3) x / <sub>Rated</sub>	3.2 8 A DC	8 A DC
1.6 A	Туре С	5SY4 115-7	DC: 5 14 (AC: 5 10) x <i>I</i> <sub>rated</sub>	8 22.4 A DC	22.4 A DC
2 A	Туре А	5SY4 102-5	DC: 2 5 (AC: 2 3) × / <sub>Rated</sub>	4 10 A DC	10 A DC
2 A	Туре С	5SY4 102-7	DC: 5 14 (AC: 5 10) x <i>I</i> <sub>Rated</sub>	10 28 A DC	28 A DC
3 A	Туре А	5SY4 103-5	DC: 2 5 (AC: 2 3) x / <sub>Bated</sub>	6 15 A DC	15 A DC
3 A	Туре С	5SY4 103-7	DC: 5 14 (AC: 5 10) x / <sub>Rated</sub>	15 42 A DC	42 A DC
4 A	Туре А	5SY4 104-5	DC: 2 5 (AC: 2 3) x / <sub>Rated</sub>	8 20 A DC	20 A DC
4 A	Туре С	5SY4 104-7	DC: 5 14 (AC: 5 10) x / <sub>Rated</sub>	20 56 A DC	56 A DC
6 A	Туре А	5SY4 106-5	DC: 2 5 (AC: 2 3) x / <sub>Rated</sub>	12 30 A DC	30 A DC
6 A	Туре В	5SY4 106-6	DC: 3 7 (AC: 3 5) × / <sub>Rated</sub>	18 42 A DC	42 A DC
6 A	Туре С	5SY4 106-7	DC: 5 14 (AC: 5 10) x <i>I</i> <sub>Rated</sub>	30 84 A DC	84 A DC
8 A	Туре А	5SY4 108-5	DC: 2 5 (AC: 2 3) × / <sub>Rated</sub>	16 40 A DC	40 A DC
8 A	Туре С	5SY4 108-7	DC: 5 14 (AC: 5 10) x <i>I</i> <sub>Rated</sub>	40 112 A DC	112 A DC
10 A	Туре А	5SY4 110-5	DC: 2 5 (AC: 2 3) × / <sub>Rated</sub>	20 50 A DC	50 A DC
10 A	Туре В	5SY4 110-6	DC: 3 7 (AC: 3 5) × / <sub>Rated</sub>	30 70 A DC	70 A DC
10 A	Туре С	5SY4 110-7	DC: 5 14 (AC: 5 10) x <i>I</i> <sub>Rated</sub>	50 140 A DC	140 A DC
13 A	Туре А	5SY4 113-5	DC: 2 5 (AC: 2 3) × / <sub>Rated</sub>	26 65 A DC	65 A DC
13 A	Туре В	5SY4 113-6	DC: 3 7 (AC: 3 5) × / <sub>Rated</sub>	39 91 A DC	91 A DC
13 A	Туре С	5SY4 113-7	DC: 5 14 (AC: 5 10) x / <sub>Rated</sub>	65 182 A DC	182 A DC
16 A	Туре А	5SY4 116-5	DC: 2 5 (AC: 2 3) × / <sub>Rated</sub>	32 80 A DC	80 A DC
16 A	Туре В	5SY4 116-6	DC: 3 7 (AC: 3 5) × / <sub>Rated</sub>	48 112 A DC	112 A DC
16 A	Туре С	5SY4 116-7	DC: 5 14 (AC: 5 10) x / <sub>Rated</sub>	80 224 A DC	224 A DC

11

### Overview (continued)

# Miniature circuit breakers acc. to EN 60898 (DIN VDE 0641-11) in 24 V DC circuits, which are powered by SITOP modular or SITOP smart power supplies <sup>1)</sup>

Article No.	Iout rated	I <sub>out dyn.</sub>	Character	istic A								
			1 A	1.6 A	2 A	3 A	4 A	6 A	8 A	10 A	13 A	16 A
6EP1332-2BA20	2.5 A	9 A/ 800 ms	✓	~	•	Х	Х	Х	Х	Х	Х	Х
6EP1333-2BA20	5 A	18 A/ 800 ms	✓	~	~	~	•	Х	Х	Х	Х	Х
6EP1333-3BA10	5 A	15 A/ 25 ms	~	~	~	•	•	Х	Х	Х	Х	х
6EP3333-8SB00-0AY0	5 A	15 A/ 25 ms	✓	~	~	•	•	Х	Х	Х	Х	Х
6EP1334-2BA20	10 A	32 A/ 1000 ms	~	~	~	~	$\checkmark$	~	•	Х	Х	х
6EP1334-3BA10	10 A	30 A/ 25 ms	✓	~	~	~	~	~	•	Х	Х	Х
6EP3334-8SB00-0AY0	10 A	30 A/ 25 ms	~	~	~	~	$\checkmark$	~	•	Х	Х	х
6EP1434-2BA10	10 A	16 A/ 100 ms	✓	~	~	~	•	Х	Х	Х	Х	х
6EP1336-2BA10	20 A	35 A/ 100 ms	✓	~	~	~	~	~	•	•	Х	Х
6EP1336-3BA10	20 A	60 A/ 25 ms	✓	~	~	~	~	~	~	✓	•	•
6EP3436-8SB00-0AY0	20 A	60 A/ 25 ms	~	~	~	~	$\checkmark$	~	~	~	•	•
6EP1436-2BA10	20 A	35 A/ 100 ms	~	~	~	~	~	~	•	•	Х	Х
6EP3337-8SB00-0AY0	40 A	120 A/ 25 ms	~	~	~	~	~	~	~	~	~	$\checkmark$
6EP1437-2BA20	40 A	65 A/ 120 ms	✓	~	~	~	~	~	~	~	~	•
6EP3437-8SB00-0AY0	40 A	120 A/ 25 ms	✓	~	~	~	~	~	~	✓	~	✓

Iout rated: Rated output current

Iout dyn: Dynamic overcurrent with short-circuit during operation

 instantaneous tripping, as dynamic overcurrent on short-circuit > limit current of electromagnetic tripping.

•: instantaneous tripping probable, as dynamic overcurrent on short-circuit at least 50% within tolerance range of the tripping characteristic.

X: no instantaneous tripping.

<sup>1)</sup> The selection of miniature circuit breakers that can be tripped is based on the consideration of the maximum possible short-circuit current of the power supply and the respective tripping characteristic at +20 °C. Further parameters that may be relevant in practice, such as self-heating, increased ambient temperature, line impedance and possibly currents flowing in parallel feeders, have not been taken into consideration.

### Fusing of the output circuit 24 V DC, selectivity

### **Overview** (continued)

Article No.	Iout rated	I <sub>out dyn.</sub>	Characteristic B			
			6 A	10 A	13 A	16 A
6EP1332-2BA20	2.5 A	9 A/ 800 ms	Х	Х	Х	Х
6EP1333-2BA20	5 A	18 A/ 800 ms	Х	Х	х	Х
6EP1333-3BA10	5 A	15 A/ 25 ms	Х	Х	Х	Х
6EP3333-8SB00-0AY0	5 A	15 A/ 25 ms	Х	Х	Х	Х
6EP1334-2BA20	10 A	32 A/ 1000 ms	•	Х	Х	Х
6EP1334-3BA10	10 A	30 A/ 25 ms	•	Х	Х	Х
6EP3334-8SB00-0AY0	10 A	30 A/ 25 ms	•	Х	Х	Х
6EP1434-2A10	10 A	16 A/ 100 ms	Х	Х	Х	Х
6EP1336-2BA10	20 A	35 A/ 100 ms	•	Х	Х	Х
6EP3436-8SB00-0AY0	20 A	60 A/ 25 ms	✓	•	Х	Х
6EP1336-3BA10	20 A	60 A/ 25 ms	✓	•	Х	Х
6EP1436-2BA10	20 A	35 A/ 100 ms	•	Х	Х	Х
6EP3337-8SB00-0AY0	40 A	120 A/ 25 ms	✓	$\checkmark$	$\checkmark$	$\checkmark$
6EP1437-2BA20	40 A	65 A/ 120 ms	✓	•	•	Х
6EP3437-8SB00-0AY0	40 A	120 A/ 25 ms	✓	$\checkmark$	$\checkmark$	√

Iout rated: Rated output current

Iout dyn: Dynamic overcurrent with short-circuit during operation

: instantaneous tripping, as dynamic overcurrent on short-circuit > limit current of electromagnetic tripping.

•: instantaneous tripping probable, as dynamic overcurrent on short-circuit at least 50% within tolerance range of the tripping characteristic.

X: no instantaneous tripping.

Fusing of the output circuit 24 V DC, selectivity

Article No.	Iout rated	l <sub>out dyn.</sub>	Character	istic C								
			1 A	1.6 A	2 A	3 A	4 A	6 A	8 A	10 A	13 A	16 A
6EP1332-2BA20	2.5 A	9 A/ 800 ms	Х	Х	х	х	х	х	х	х	Х	Х
6EP1333-2BA20	5 A	18 A/ 800 ms	~	•	Х	Х	х	Х	х	Х	Х	х
6EP1333-3BA10	5 A	15 A/ 25 ms	~	Х	Х	Х	Х	Х	Х	Х	Х	Х
6EP3333-8SB00-0AY0	5 A	15 A/ 25 ms	~	Х	Х	Х	Х	Х	Х	Х	Х	Х
6EP1334-2BA20	10 A	32 A/ 1000 ms	~	~	~	•	Х	Х	Х	Х	Х	Х
6EP1334-3BA10	10 A	30 A/ 25 ms	~	~	~	•	Х	Х	Х	Х	Х	Х
6EP3334-8SB00-0AY0	10 A	30 A/ 25 ms	~	~	~	•	х	Х	х	Х	Х	Х
6EP1434-2BA10	10 A	16 A/ 100 ms	~	•	Х	Х	Х	Х	Х	Х	Х	Х
6EP1336-2BA10	20 A	35 A/ 100 ms	~	~	~	•	Х	Х	Х	Х	Х	Х
6EP1336-3BA10	20 A	60 A/ 25 ms	✓	~	~	~	~	•	Х	Х	Х	Х
6EP3436-8SB00-0AY0	20 A	60 A/ 25 ms	~	~	~	~	✓	•	Х	Х	Х	Х
6EP1436-2BA10	20 A	35 A/ 100 ms	~	~	~	•	Х	Х	Х	Х	Х	Х
6EP3337-8SB00-0AY0	40 A	120 A/ 25 ms	~	~	~	~	~	~	$\checkmark$	•	Х	Х
6EP1437-2BA20	40 A	65 A/ 120 ms	✓	~	~	~	~	•	Х	Х	Х	Х
6EP3437-8SB00-0AY0	40 A	120 A/ 25 ms	~	~	~	~	✓	~	✓	•	Х	Х

# Standards and approvals

### Overview

#### Overview of important standards and approvals

EN	European standards
EN 50178	Electronic equipment for use in power installations
EN 55022	Information technology equipment - Radio disturbance characteristics - Limits and methods of measurement
EN 60079	Electrical apparatus for explosive gas atmospheres
EN 60529	Degrees of protection provided by enclosures (IP-Code)
EN 60721	Classification of environmental conditions
EN 60950-1	Information technology equipment – Safety
EN 61000-3-2	Electromagnetic compatibility (EMC) – Part 3-2: Limits for harmonic current emissions (equipment input current ≤16 A per phase)
EN 61000-6-2	Electromagnetic compatibility (EMC) – Part 6-2: Generic standards – Immunity for industrial environments
EN 61000-6-3	Electromagnetic compatibility (EMC) – Part 6-3: Generic standards – Emission standard for residential, commercial and light industrial environments
UL	Underwriters Laboratories
UL 508	Industrial control equipment
UL 1778	Uninterruptible Power Supply Equipment
UL 2367	Solid State Overcurrent Protectors
UL 60079	Electrical apparatus for explosive gas atmospheres
UL 60950 -1	Information technology equipment – Safety
ANSI	American National Standards Institute
ANSI/ISA -12.12.01	Non-Incendive Electrical Equipment for Use in Class I and II, Division 2 and Class III, Divisions 1 and 2 Hazardous (Classified) Locations
NEC	Class 2 Secondary circuit supplied by a power source complying with Article 725, Part C of the National Electrical Code (NEC), ANSI/NFPA 70
CSA	Canadian Standards Association
CSA C22.2 No. 14	Industrial control equipment
CSA C22.2 No. 142	Process control equipment
CSA C22.2 No. 107.1	General Use Power Supplies
CSA C22.2 No. 213	Non-Incendive Electrical Equipment for Use in Class I, Division 2 Hazardous Locations
CSA C22.2 No. 60079	Electrical apparatus for explosive gas atmospheres
CSA C22.2 No. 60950-1	Information technology equipment – Safety
ATEX	Equipment and protective systems intended for use in Potentially Explosive Atmospheres
IECEx	Equipment for use in Explosive Atmospheres
FM	Factory Mutual Research
SEMI	F47 Specification for semiconductor processing equipment - Voltage sag immunity
ABS	American Bureau of Shipping
BV	Bureau Veritas
DNV GL	Det Norske Veritas, Germanischer Lloyd
LR	Lloyd's Register
NK	Nippon Kaiji Kyokai

# Certificates

Certificates

					UL, CSA	L					EX				Shipb	uildir	ng		
	CE (LVD, EMC)	CB-Scheme	cULus-Listed (UL 508, CSA C22.2 No 107.1)	UL-Recognized (UL 2367)	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1)	cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	NEC class 2 (nach UL 1310)	АТЕХ	IECEX	cULus Class I, Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213)	cURus Class I, Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213)	cCSAus Class I, Div. 2 (CSA C22.2 No. 213, ANSI/ISA-12.12.01)	FM (Class I, Div. 2)	DNV GL (Det Norske Veritas Germanischer Lloyd)	ABS (American Bureau of Shipping)	BV (Bureau Veritas)	LR (Lloyd's Register)	NK (Nippon Kaiji Kyokai)	SEMI F47
SITOP PSU8600																			
6EP3436-8SB00-2AY0	Х	Х	Х			Х		Х	Х			Х		Х	Х				Х
6EP3437-8SB00-2AY0	х	Х	х			Х		Х	Х			Х		Х	Х				х
6EP3436-8MB00-2CY0	Х	Х	Х			Х		Х	Х			Х		Х	Х				Х
6EP3437-8MB00-2CY0	Х	Х	Х			Х		Х	Х			Х		Х	Х				Х
6EP4436-8XB00-0CY0	Х	Х	Х			Х		Х	Х			Х		Х	Х				
6EP4436-8XB00-0DY0	х	Х	х			Х	Х	Х	Х			Х		Х	Х				
6EP4437-8XB00-0CY0	Х	Х	Х			Х		Х	Х			Х		Х	Х				
6EP4197-8AB00-0XY0	х	Х	х			Х		Х	Х			Х							
6EP4145-8GB00-0XY0	Х	Х			Х	х		Х	Х			Х							
6EP4143-8JB00-0XY0	х	Х				Х													
6EP4297-8HB00-0XY0	х	Х	х			Х		Х	Х			Х		Х	Х				х
6EP4297-8HB10-0XY0	х	Х	х			Х		Х	Х			Х		Х	Х				х
6EP4293-8HB00-0XY0	Х	Х	Х			Х		Х	Х			Х		Х	Х				Х
6EP4295-8HB00-0XY0	Х	Х	Х			Х		Х	Х			Х		Х	Х				Х
SITOP PSU8200																			
6EP3333-8SB00-0AY0	Х	Х	Х			Х		Х	Х			Х		Х	Х				Х
6EP3334-8SB00-0AY0	Х	Х	Х			Х		Х	Х			Х		Х	Х				Х
6EP1336-3BA10	Х	Х	Х			Х		Х	Х			Х		Х	Х				
6EP3436-8SB00-0AY0	Х	Х	Х			Х		Х	Х			Х		Х	Х				Х
6EP1437-3BA10	Х	Х	Х			Х		Х	Х			Х		Х	Х				Х
6EP3337-8SB00-0AY0	Х	Х	Х			Х		Х	Х	Х		Х		Х	Х				
6EP1337-3BA00	Х		Х					Х	Х			Х							
6EP1333-3BA10	Х	Х	Х			Х		Х	Х			Х		Х	Х				Х
6EP1333-3BA10-8AC0	Х		Х					Х	Х			Х		Х	Х				
6EP1334-3BA10	Х	Х	Х			Х		Х	Х			Х		Х	Х				х
6EP1334-3BA10-8AB0	х		х					Х	Х			Х		Х	Х				
6EP1457-3BA00	Х		Х			Х								Х	Х				
6EP3446-8SB10-0AY0	х	Х	х			Х		Х	Х			Х							
6EP3446-8SB00-0AY0	Х	Х	Х			Х		Х	Х			Х		Х	Х				Х
6EP3437-8SB00-0AY0	Х	Х	Х			Х		Х	Х			Х		i. p.	i. p.				Х
6EP3447-8SB00-0AY0	Х	Х	Х			Х		Х	Х			Х							Х

# Certificates

# Certificates (continued)

					UL, CSA						EX				Shipb	uildir	ng		
	CE (LVD, EMC)	CB-Scheme	cULus-Listed (UL 508, CSA C22.2 No 107.1)	UL-Recognized (UL 2367)	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1)	cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	NEC class 2 (nach UL 1310)	АТЕХ	IECEX	cULus Class I, Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213)	cURus Class I, Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213)	cCSAus Class I, Div. 2 (CSA C22.2 No. 213, ANSI/ISA-12.12.01)	FM (Class I, Div. 2)	DNV GL (Det Norske Veritas Germanischer Lloyd)	ABS (American Bureau of Shipping)	BV (Bureau Veritas)	LR (Lloyd's Register)	NK (Nippon Kaiji Kyokai)	SEMI F47
SITOP PSU6200																			
6EP3321-7SB00-0AX0	Х	Х	Х			Х				i. p.				i. p.	i. p.				Х
6EP3323-7SB00-0AX0	Х	Х	Х			Х				i. p.				i. p.	i. p.				Х
6EP3324-7SB00-3AX0	Х	Х	Х			Х				i. p.				i. p.	i. p.				Х
6EP3331-7SB00-0AX0	Х	Х	Х			Х				i. p.				i. p.	i. p.				Х
6EP3332-7SB00-0AX0	Х	Х	Х			Х				i. p.				i. p.	i. p.				Х
6EP3333-7SB00-0AX0	Х	Х	Х			Х				i. p.				i. p.	i. p.				Х
6EP3333-7SB10-0AX0	Х	Х	Х			i. p.	Х			i. p.				i. p.	i. p.				Х
6EP3334-7SB00-3AX0	Х	Х	Х			Х				i. p.				i. p.	i. p.				Х
6EP3336-7SB00-3AX0	Х	Х	Х			i. p.				i. p.				i. p.	i. p.				Х
SITOP smart																			
6EP1322-2BA00	Х	Х	Х			Х		Х	Х	Х		Х		Х					
6EP1323-2BA00	Х	Х	Х			Х		Х	Х	Х		Х		Х					
6EP1332-2BA20	Х	Х	Х			Х		Х	Х	Х		Х		Х		Х			
6EP1333-2BA20	Х	Х	Х			Х		Х	Х	Х		Х		Х		Х			
6EP1334-2BA20	Х	Х	Х			Х		Х	Х	Х		Х		Х		Х			
6EP1336-2BA10	Х	Х	Х			Х		Х	Х			Х		Х					
6EP1433-2BA20	Х	Х	Х			Х		Х	Х	Х				Х	Х				
6EP1434-2BA20	Х	Х	Х			Х		Х	Х	Х				Х	Х				
6EP1436-2BA10	х	Х	Х			Х		Х	Х			Х		Х	Х				
6EP1437-2BA20	х	Х	Х			Х		Х	Х			Х		Х	Х				
SITOP lite																			
6EP1332-1LB00	Х	Х	Х																
6EP1333-1LB00	Х	Х	Х																
6EP1334-1LB00	х	Х	Х																
6EP1336-1LB00	х	Х	Х																
LOGO!Power																			
6EP3310-6SB00-0AY0	х	Х	Х			х	Х	Х	Х	х			Х	Х	Х				х
6EP3311-6SB00-0AY0	х	Х	Х			Х		Х	Х	Х			Х	Х	Х				х
6EP3320-6SB00-0AY0	х	Х	х			Х	Х	Х	Х	Х			Х	Х	Х				х
6EP3321-6SB00-0AY0	х	Х	х			Х	Х	х	Х	Х			Х	х	Х				х
6EP3322-6SB00-0AY0	х	Х	х			Х	Х	х	Х	Х			Х	х	Х				х
6EP3321-6SB10-0AY0	х	Х	х			Х	Х	х	Х	Х			Х	х	Х				х
6EP3322-6SB10-0AY0	х	Х	х			Х	Х	х	Х	Х			Х	х	Х				х
6EP3330-6SB00-0AY0	х	Х	х			Х	Х	х	Х	Х			Х	х	Х				x
6EP3331-6SB00-0AY0	х	х	х			Х	Х	х	Х	Х			Х	х	Х				x
6EP3332-6SB00-0AY0	х	х	х			Х	Х	х	Х	Х			Х	х	Х				х
6EP3333-6SB00-0AY0	х	х	х			Х		х	Х	Х			Х	х	Х				x
	1																		

Certificates

# Certificates (continued)

					UL, CSA						EX				Shipb	uildir	ng		
	CE (LVD, EMC)	CB-Scheme	cULus-Listed (UL 508, CSA C22.2 No 107.1)	UL-Recognized (UL 2367)	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1)	cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	NEC class 2 (nach UL 1310)	АТЕХ	IECEX	cULus Class I, Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213)	cURus Class I, Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213)	cCSAus Class I, Div. 2 (CSA C22.2 No. 213, ANSI/ISA-12.12.01)	FM (Class I, Div. 2)	DNV GL (Det Norske Veritas Germanischer Lloyd)	ABS (American Bureau of Shipping)	BV (Bureau Veritas)	LR (Lloyd's Register)	NK (Nippon Kaiji Kyokai)	SEMI F47
SITOP compact																			
6EP1321-5BA00	Х	Х	Х			Х		Х	Х			Х		Х	Х				
6EP1322-5BA10	Х	Х	Х			Х		Х	Х			Х		Х	Х				
6EP1331-5BA00	Х	Х	Х				Х	Х	Х			Х		Х	Х				
6EP1331-5BA10	Х	Х	Х				Х	Х	Х			Х		Х	Х				
6EP1332-5BA00	Х	Х	Х				Х	Х	Х			Х		Х	Х				
6EP1332-5BA20	Х	Х	Х				Х	Х	Х			Х		Х	Х				
6EP1332-5BA10	Х	Х	Х			Х		Х	Х			Х		Х	Х				
SIMATIC-Design power supplies																			
6ES7307-1BA01-0AA0	x	х						х		Х			Х	х	х	х	Х	х	
6ES7305-1BA80-0AA0	x		х																
6ES7307-1EA01-0AA0	x	х						х		Х			Х	х	х	х	Х	х	
6ES7307-1EA80-0AA0	x		х																
6ES7307-1KA02-0AA0	x	х						Х		Х			Х	х	Х	Х	Х	х	
6EP1332-1SH71	x	х	х					Х		Х			Х	х	Х	Х	Х	х	
6EP1332-4BA00	X	х						Х		х			Х	х	Х	Х	Х	х	
6EP1333-4BA00	x	х						Х		Х			Х	х	Х	Х	Х	х	
6ES7148-4PC00-0HA0	х		Х																
6EP7133-6AB00-0BN0	х	х				Х		Х	Х	Х				Х					
6EP7133-6AE00-0BN0	х	х				Х		Х	Х	Х				Х					
DC/DC-Converter																			
6EP1731-2BA00	х		Х																
6EP1732-0AA00	х		Х																
6EP1621-2BA00	х		Х			Х													
6EP1536-3AA00	X	Х	Х											Х					
6EP3124-0TA00-0AY0	х	Х	Х											Х	i. p.				
6EP3134-0TA00-0AY0	x	Х	х											х	i. p.				
6EP3234-0TA00-0AY0	x	Х	Х											Х	i. p.				
6EP3133-0TA10-0AY0	x	Х	Х											Х	i. p.				
6EP3123-0TA00-0AY0	x	Х	х											х	i. p.				
6EP3133-0TA00-0AY0	x	Х	Х											Х	i. p.				
6EP3233-0TA10-0AY0	x	Х	Х											Х	i. p.				
6EP3233-0TA00-0AY0	х	х	Х											Х	i. p.				

# Certificates

# Certificates (continued)

					UL, CSA	<b>\</b>					EX				Shipb	uildir	ıg		
	CE (LVD, EMC)	CB-Scheme	cULus-Listed (UL 508, CSA C22.2 No 107.1)	UL-Recognized (UL 2367)	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1)	cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	NEC class 2 (nach UL 1310)	АТЕХ	IECEX	cULus Class I, Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213)	cURus Class I, Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213)	cCSAus Class I, Div. 2 (CSA C22.2 No. 213, ANSI/ISA-12.12.01)	FM (Class I, Div. 2)	DNV GL (Det Norske Veritas Germanischer Lloyd)	ABS (American Bureau of Shipping)	BV (Bureau Veritas)	LR (Lloyd's Register)	NK (Nippon Kaiji Kyokai)	SEMI F47
Special desgins and uses																			
Wall mounting																			
6EP1321-1LD00	Х	Х	Х																
6EP1322-1LD00	Х	Х	Х																
6EP1331-1LD00	Х	Х	Х																
6EP1332-1LD00	Х	Х	Х																
6EP1332-1LD10	Х	Х	Х																
6EP1333-1LD00	Х	Х	Х																
6EP1334-1LD00	Х	Х	Х																
High degree of protection																			
6EP1333-7CA00	Х		Х																
6EP1334-7CA00	Х		Х																
6ES7148-4PC00-0HA0	Х		Х																
Battery charging																			
6EP3424-8UB00-0AY0	Х	Х	Х			Х		Х	Х			Х		Х	Х				
6EP3436-8UB00-0AY0	Х	Х	Х			Х		Х	Х			Х		Х	Х				
6EP3437-8UB00-0AY0	Х	Х	Х			Х		Х	Х			Х							Х
6EP1437-3BA20	Х		Х			Х													
Medical applications																			
6EP4333-0SB00-0AY0																			
6EP4436-0SB00-0AY0																			
Alternative output voltages																			
6EP3323-0SA00-0BY0	х		Х				Х												
6EP3343-0SA00-0AY0	х		х																
Special applications																			
6EP1333-1AL12	х		х																
6EP1334-1AL12	х		х																
6EP1433-0AA00	Х		х																

Certificates

# Certificates (continued)

					UL, CSA						EX				Shipb	uildir	ng		
	CE (LVD, EMC)	CB-Scheme	cULus-Listed (UL 508, CSA C22.2 No 107.1)	UL-Recognized (UL 2367)	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1)	cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	NEC class 2 (nach UL 1310)	АТЕХ	IECEX	cULus Class I, Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213)	cURus Class I, Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213)	cCSAus Class I, Div. 2 (CSA C22.2 No. 213, ANSI/ISA-12.12.01)	FM (Class I, Div. 2)	DNV GL (Det Norske Veritas Germanischer Lloyd)	ABS (American Bureau of Shipping)	BV (Bureau Veritas)	LR (Lloyd's Register)	NK (Nippon Kaiji Kyokai)	SEMI F47
SITOP DC-USV with capacitors																			
6EP1933-2EC41	Х	Х	Х			Х		Х				Х		Х	Х				
6EP1933-2EC51	Х	Х	Х			Х		Х				Х		Х	Х				
6EP1935-5PG01	Х	Х	Х			Х		Х				Х		Х	Х				
SITOP DC-USV with battery modules																			
6EP4134-3AB00-0AY0	х	х	х					х	Х	Х		Х		х	Х				1
6EP4134-3AB00-1AY0	х	х	х					х	Х	Х		Х		х	Х				
6EP4134-3AB00-2AY0	х	х	х					Х	Х	Х		Х		х	Х				1
6EP4136-3AB00-0AY0	х	х	х					х	Х	Х		Х		х	Х				
6EP4136-3AB00-1AY0	х	х	х					х	Х	Х		Х		х	Х				
6EP4136-3AB00-2AY0	х	х	х					х	Х	Х		Х		х	Х				
6EP4137-3AB00-0AY0	х	х	х					Х	Х	Х		Х		х	Х				1
6EP4137-3AB00-1AY0	х	Х	х					Х	Х	Х		Х		х	Х				
6EP4137-3AB00-2AY0	х	Х	х					Х	Х	Х		Х		х	Х				1
6EP4131-0GB00-0AY0	х	Х			х			X <sup>1)</sup>	X <sup>1)</sup>		Х	Х		Х	Х				
6EP4133-0GB00-0AY0	х	Х			Х			X <sup>1)</sup>	X <sup>1)</sup>		Х	Х		Х	Х				1
6EP4134-0GB00-0AY0	х	Х			х			X <sup>1)</sup>	X <sup>1)</sup>		Х	Х		Х	Х				
6EP4135-0GB00-0AY0	х	Х			Х			X <sup>1)</sup>	X <sup>1)</sup>		Х	Х		Х	Х				1
6EP4132-0GB00-0AY0	х	Х			Х			X <sup>1)</sup>	X <sup>1)</sup>		Х	Х		Х	Х				
6EP4133-0JB00-0AY0	х	Х			Х									Х	Х				
6EP1931-2DC21	х		Х					Х				Х		Х	Х				1
6EP1931-2DC31	Х		Х					Х				Х		Х	Х				
6EP1931-2DC42	х		Х					Х				Х		Х	Х				1
6EP1931-2EC21	Х		Х					Х				Х		Х	Х				
6EP1931-2EC31	Х		Х					Х				Х		Х	Х				1
6EP1931-2EC42	Х		Х					Х				Х		Х	Х				
6EP1931-2FC21	Х		Х					Х				Х		Х	Х				
6EP1931-2FC42	Х		Х					Х				Х		Х	Х				
6EP1935-6MC01	Х				Х			X <sup>1)</sup>				Х		Х	Х				
6EP1935-6MD31	Х				Х			X <sup>1)</sup>				Х		Х	Х				
6EP1935-6MD11	Х				Х			X <sup>1)</sup>				Х		Х	Х				
6EP1935-6ME21	Х				Х			X <sup>1)</sup>				Х		Х	Х				
6EP1935-6MF01	Х				Х			X <sup>1)</sup>				Х		Х	Х				I

<sup>1)</sup> The ATEX and IECEx Directives require that UPS batteries are not connected in parallel (with increased capacity).

# Certificates

### Certificates (continued)

					UL, CSA						EX				Shipb	uildin	g		
	CE (LVD, EMC)	CB-Scheme	cULus-Listed (UL 508, CSA C22.2 No 107.1)	UL-Recognized (UL 2367)	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1)	cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)	NEC class 2 (nach UL 1310)	АТЕХ	IECEX	cULus Class I, Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213)	cURus Class I, Div. 2 (ANSI/ISA-12.12.01, CSA C22.2 No. 213)	cCSAus Class I, Div. 2 (CSA C22.2 No. 213, ANS//SA-12.12.01)	FM (Class I, Div. 2)	DNV GL (Det Norske Veritas Germanischer Lloyd)	ABS (American Bureau of Shipping)	BV (Bureau Veritas)	LR (Lloyd's Register)	NK (Nippon Kaiji Kyokai)	SEMI F47
Add-on modules																			
6EP1961-3BA21	Х		Х					Х	Х			Х		Х	Х				1
6EP1962-2BA00	Х		Х				Х												
6EP1964-2BA00	Х		Х																
6EP4346-7RB00-0AX0	Х	Х	Х			i. p.		i. p.	i. p.					i. p.	i. p.				1
6EP4347-7RB00-0AX0	Х	Х	Х			i. p.		i. p.	i. p.					i. p.	i. p.				1
6EP1961-2BA11	Х	Х	Х	Х				Х	Х			Х		Х	Х				
6EP1961-2BA31	Х	Х	Х	Х				Х	Х			Х		Х	Х				1
6EP1961-2BA21	Х	Х	Х	Х				Х	Х			Х		Х	Х				1
6EP1961-2BA41	Х	Х	Х	Х				Х	Х			Х		Х	Х				1
6EP1961-2BA00	Х		Х	Х				Х				Х							1
6EP1961-2BA51	Х	Х	Х	Х			Х	Х	Х			Х		Х	Х				1
6EP1961-2BA61	Х	Х	Х	Х			Х	Х	Х			Х		Х	Х				
6EP4438-7EB00-3DX0	Х	Х	Х	i. p.		i. p.		i. p.	i. p.	i. p.				i. p.	i. p.				
6EP4438-7FB00-3DX0	Х	Х	Х	i. p.		i. p.		i. p.	i. p.	i. p.				i. p.	i. p.				
6EP1961-3BA01	Х		Х	Х				Х	Х			Х		Х	Х				
6EP1967-2AA00	Х		Х	Х															
6EP4683-6LB00-0AY0	Х	Х	Х	Х															I

© Siemens 2019

# Appendix



	2
N – Digital	Industry Academy
s at Sieme	ens

2/2	SITRAIN – Digital Industry Academy
<b>2/3</b> 2/4	Partners at Siemens Siemens Partner Program
<b>2/5</b> 2/5	Siemens Automation Cooperates with Education (SCE) Teaching made easy - Comprehensive support on the way to Industry 4.0
<b>2/8</b> 2/9 2/11	Industry Services Industry Services – Portfolio overview Online Support
2/12	Conditions of sale and delivery


1

# Appendix SITRAIN – Digital Industry Academy



#### Time for learning

Today's demands on our knowledge are every bit as diverse and dynamic as our profession itself. We keep learning more and longer - for our work, for our career and for ourselves. Advancing digitalization entails new topics and is also changing the way we absorb and process knowledge. SITRAIN - Digital Industry Academy offers the right source of knowledge here, which we can use anytime in just the way we need it. The time for learning is now.



#### Knowledge for every need

With its three areas - SITRAIN open, SITRAIN access and SITRAIN personal - SITRAIN offers you an all-encompassing range of options for an ongoing expansion of your knowledge and skills, suited for every type of learner. And SITRAIN uses advancing digitalization to continuously expand content and offer new training methods.



### SITRAIN – Digital Industry Academy Customer Support Germany

Tel.: +49 911 895-7575 E-Mail: sitrain.digital.industry.academy.de@siemens.com

#### Knowledge you can always find

SITRAIN open bundles useful information, worthwhile data and up-to-date expert knowledge about Siemens products for industry. Search it anytime, find anything - and always the right stuff

#### Knowledge that gets you ahead

SITRAIN access is learning in the digital age. It offers you individualized ways to build your knowledge and access to exclusive digital training courses. Take advantage of sustainable learning success with a wide range of learning methods. Improve your skills - whether working in groups with others, or by yourself. Whenever, wherever and however you need to.

#### Knowledge you can experience


We all want to learn from the best. And SITRAIN personal's training courses let you benefit from our well-practiced trainers' expert knowledge, along with direct access to our training equipment. That's the best way to convey knowledge - whether at your company or in our training classrooms.

#### SITRAIN – Digital Industry Academy

www.siemens.com/sitrain

- SITRAIN open: www.siemens.com/sitrain-open
- SITRAIN access: www.siemens.com/sitrain-access
- SITRAIN personal: www.siemens.com/sitrain-personal

#### Partner at Siemens



At your service locally, around the globe for consulting, sales, training, service, support, spare parts on the entire portfolio of Digital Industries.

Your partner can be found in our Personal Contacts Database at: www.siemens.com/automation-contact

You start by selecting

- the required competence,
- products and branches,
- a country and a city

or by a

• location search or free text search.

### Appendix

Partner at Siemens

#### **Siemens Partner Program**

#### Overview

# Siemens Solution and Approved Partner – Partners for your success



#### Highest competence in automation and drive technology

Siemens works closely together with selected partner companies around the world in order to ensure that customer requirements for all aspects of automation and drives are fulfilled as best as possible – wherever you are, and whatever the time.

We place great value on our customers acting in accordance with the same ideals which characterize Siemens as a whole: Competence, professionalism and quality. That is why continuous development through qualification and certification measures in line with global standards is a central aspect of our Partner Program. This means that with our partners, you benefit from the same high quality standards all over the world. The partner emblem is the symbol for tried and tested quality.

#### The partner network for industry

The Siemens Partner Program offers you expertise and experience close at hand.

Within our global network, we distinguish between Solution Partners and Approved Partners. We currently work with more than 1,500 Solution Partners around the world. Our network of over 150 Approved Partners continues to grow. In more than 80 countries worldwide

#### Siemens Solution Partner – Automation Drives



At present we are working with more than 1,500 Solution Partners worldwide. They are characterized by extensive application, system and sector knowledge, as well as proven project experience, and are able to implement future-proof tailored solutions of the highest quality, based on our product and system portfolio.

#### Siemens Approved Partner – Value Added Reseller



With their detailed technical knowledge, Siemens Approved Partners – Value Added Resellers offer a combination of products and services that range from specialist technologies and customized modifications to the provision of highquality system and product packages. They also provide qualified technical support and assistance.

### Siemens Approved Partner – Industry Services



Siemens Approved Partner – Industry Services put their unique expertise entirely at the service of enhancing your productivity and can be instrumental in ensuring the availability of your plants.

#### Partner Finder

The ideal partner for your task is just a mouse click away!



In the Siemens global Solution Partner program, customers are certain to find the optimum partner for their specific requirements – with no great effort. The Partner Finder is basically a comprehensive database that showcases the profiles of all our partners.

#### Easy selection:

Set filters in the search screen form according to the criteria that are relevant to you. You can also directly enter the name of an existing partner.

#### Skills at a glance:

Gain a quick insight into the specific competencies of any particular partner with the reference reports.

Direct contact option: Use our electronic query form:

www.siemens.com/partnerfinder

Additional information of the Siemens Parners for industry is available online at:

www.siemens.com/partnerprogram

### Appendix Siemens Automation Cooperates with Education (SCE)

Teaching made easy - Comprehensive support on the way to Industry 4.0

#### Knowledge & technology – the keystones to success in digitalization



#### Digitalization is quickly and radically changing our world. What does this mean for education?

In the world of Industry 4.0, companies can expect a host of new opportunities and challenges. New systems are verified on the spot through simulations. Automated mass production processes can make every product on the conveyor belt a unique product.




New products are now market-ready much faster. Siemens is shaping this transformation as a technology leader in the field of automation and process lifecycle management (PLM).

These new digitalization processes are changing the know-how requirements for employees. Many educational institutions are facing the challenge of conveying Industry 4.0 know-how as part of their teaching and training. The Siemens Automation Cooperates with Education (SCE) program is supporting educators on the way to Industry 4.0.

#### The SCE digitalization concept for educators

The SCE digitalization concept presented here shows how digitalization can be implemented in educational institutions – from vocational schools to universities. Digitalization (or Industry 4.0) know-how is now introduced through CAx and cloud technologies. It is founded on the basics of automation, such as digital technologies, PLC and information technologies, and on advanced automation and industrial communication technologies.


The level of digitalization knowledge can be weighted, depending on the vocational field or branch of study – e.g. mechanical engineering, automation engineering or computer science.



### Appendix Siemens Automation Cooperates with Education (SCE)

#### Teaching made easy - Comprehensive support on the way to Industry 4.0

#### The SCE digitalization concept for educators (continued)



As part of their project work, students at Vocational School 2 in Wolfsburg, Germany, have implemented the three levels of the SCE Industry 4.0 concept. A virtual twin created with the Siemens NX Mechatronics Designer (MCD) CAD software was used for the design and virtual commissioning. This enables fast and efficient assembly of the real automation system, e.g. with SIMATIC S7-1500/ET 200SP/RFID, for use in classes. Production data, such as the number of bottles filled, production date and system parameters, are uploaded to a cloud using SIMATIC IOT2000.

siemens.com/iot2020

siemens.com/nx

#### The SCE offers



#### Learning and training documents

More than 100 didactically prepared learning and training documents are available through SCE and incorporate the digitalization concept. They are designed for use in classes, but can also be customized or used for individual study. These documents are available for free download, most of them in 7 languages.

siemens.com/sce/documents

#### Educator courses

Excellent teaching content is needed to introduce students to digitalization. For this purpose, SCE holds educator courses in certain regions. Based on our learning and training documents and through practical exercises, educators acquire the latest Industry 4.0 know-how.

siemens.com/sce/courses



#### Trainer packages

The 90 SCE trainer packages help educators teaching and implementing the SCE digitalization concept. Trainer packages comprise specially compiled, genuine Siemens hardware and software products. The trainer packages are based on the learning and training documents and are offered to schools, colleges and universities at special terms.

siemens.com/sce/tp

#### Support for your projects / textbooks

We support you on selected projects with advice and assistance from SCE contact partners.

As a special service, we support textbook authors. We maintain a list of textbooks on the SCE website.

siemens.com/sce/contact

siemens.com/sce/books

Teaching made easy - Comprehensive support on the way to Industry 4.0

### Partnerships for proliferation of Industry 4.0 in education





#### Partnership with WorldSkills

As a technology powerhouse, we support vocational training of students around the world. Since 2010, we have partnered with WorldSkills as a Global Industry Partner in order to amplify this cause.

WorldSkills is an international organization whose mission is to raise the profile and recognition of skilled people, and show how important vocational skills are in achieving economic growth and personal success. Every two years, WorldSkills hosts the world championships of skills.

Siemens provides the competitors with automation products, such as SIMATIC S7-1500 and LOGO!, for the disciplines: industrial control, electrical installations, Polymechanics/Automation and manufacturing technology.

The next international skill competitions are scheduled for Kazan/Russia, in 2019 and Shanghai/China, in 2021. Additionally, we support selected continental and regional competitions.

siemens.com/worldskills

#### Partnerships with educators

We provide support to educators and educational organizations in the form of one-on-one advice through SCE contact partners and Siemens experts as well as long-term cooperation.

siemens.com/sce/contact

#### Partnerships with producers of learning systems

For practical training in classrooms and labs, numerous producers of learning systems offer a wide range of complete didactic solutions based on SCE trainer packages.

siemens.com/sce/partner

### Information portal



To facilitate your teaching assignment and/or for selfstudy, we offer educators and students a comprehensive SCE information portal. At this portal you have quick access to all SCE offers, e.g. learning and training documents including projects, Getting Started information, videos, manuals, trial software and newsletters.

siemens.com/sce





© Siemens 2019

### Appendix

**Industry Services** 



#### Keep your business running and shaping your digital future – with Industry Services

Optimizing the productivity of your equipment and operations can be a challenge, especially with constantly changing market conditions. Working with our service experts makes it easier. We understand your industry's unique processes and provide the services needed so that you can better achieve your business goals.

You can count on us to maximize your uptime and minimize your downtime, increasing your operations' productivity and reliability. When your operations have to be changed quickly to meet a new demand or business opportunity, our services give you the flexibility to adapt. Of course, we take care that your production is protected against cyber threats. We assist in keeping your operations as energy and resource efficient as possible and reducing your total cost of ownership. As a trendsetter, we ensure that you can capitalize on the opportunities of digitalization and by applying data analytics to enhance decision making: You can be sure that your plant reaches its full potential and retains this over the longer lifespan.

You can rely on our highly dedicated team of engineers, technicians and specialists to deliver the services you need - safely, professionally and in compliance with all regulations. We are there for you, where you need us, when you need us.

www.siemens.com/industryservices

#### Overview



Digital Industry Services make your industrial processes transparent to gain improvements in productivity, asset availability, and energy efficiency.

Production data is generated, filtered and translated with intelligent analytics to enhance decision-making.

This is done whilst taking data security into consideration and with continuous protection against cyber-attack threats.

https://www.siemens.com/global/en/home/products/services/ industry/digital-services.html





From the basics and advanced to specialist skills, SITRAIN courses provide expertise right from the manufacturer – and encompass the entire spectrum of Siemens products and systems for the industry.

Worldwide, SITRAIN courses are available wherever you need a training course in more than 170 locations in over 60 countries.

https://support.industry.siemens.com/cs/ww/en/sc/2226



**Industry Online Support** site for comprehensive information, application examples, FAQs and support requests.

**Technical and Engineering Support** for advice and answers for all inquiries about functionality, handling, and fault clearance. The Service Card as prepaid support for value added services such as Priority Call Back or Extended Support offers the clear advantage of quick and easy purchasing.

**Information & Consulting Services**, e.g. SIMATIC System Audit; clarity about the state and service capability of your automation system or Lifecycle Information Services; transparency on the lifecycle of the products in your plants.

https://support.industry.siemens.com/cs/ww/en/sc/2235



Spare Parts Services are available worldwide for smooth and fast supply of spare parts – and thus optimal plant availability. Genuine spare parts are available for up to ten years. Logistic experts take care of procurement, transport, custom clearance, storage and order management. Reliable logistics processes ensure that components reach their destination as needed.

Since not all spare parts can be kept in stock at all times, Siemens offers a preventive measure for spare parts provisioning on the customer's premises with optimized **Spare Parts Packages** for individual products, custom-assembled drive components and entire integrated drive trains – including risk consulting.

**Asset Optimization Services** help you design a strategy for parts supply where your investment and carrying costs are reduced and the risk of obsolescence is avoided.

https://support.industry.siemens.com/cs/ww/en/sc/2110

# Appendix

**Industry Services** 

#### Industry Services – Portfolio overview

**Overview** (continued)



Repair Services are offered on-site and in regional repair centers for fast restoration of faulty devices' functionality.

Also available are extended repair services, which include additional diagnostic and repair measures, as well as emergency services.

https://support.industry.siemens.com/cs/ww/en/sc/2154



Provide a cost-effective solution for the expansion of entire plants, optimization of systems or upgrading existing products to the latest technology and software, e.g. migration services for automation systems.

Service experts support projects from planning through commissioning and, if desired over the entire extended lifespan, e.g. Retrofit for Integrated Drive Systems for an extended lifetime of your machines and plants.

https://support.industry.siemens.com/cs/ww/en/sc/2286



Siemens specialists are available globally to provide expert field and maintenance services, including commissioning, functional testing, preventive maintenance and fault clearance. All services can be included in customized service agreements with defined reaction times or fixed maintenance intervals.

https://support.industry.siemens.com/cs/ww/en/sc/2265



A technical Service Program or Agreement enables you to easily bundle a wide range of services into a single annual or multiyear agreement.

You pick the services you need to match your unique requirements or fill gaps in your organization's maintenance capabilities.

Programs and agreements can be customized as KPI-based and/or performance-based contracts.

https://support.industry.siemens.com/cs/ww/en/sc/2275

**Online Support** 

### Overview



Siemens Industry and Online Support with some 1.7 million visitors per month is one of the most popular web services provided by Siemens. It is the central access point for comprehensive technical know-how about products, systems and services for automation and drives applications as well as for process industries. In connection with the challenges and opportunities related to digitalization you can look forward to continued support with innovative offerings.

### Appendix

Conditions of sale and delivery

#### 1. General Provisions

By using this catalog you can purchase products (hardware, software and services) described therein from Siemens Aktiengesellschaft subject to the following Terms and Conditions of Sale and Delivery (hereinafter referred to as "T&C"). Please note that the scope, the quality and the conditions for supplies and services, including software products, by any Siemens entity having a registered office outside Germany, shall be subject exclusively to the General Terms and Conditions of the respective Siemens entity. The following T&C apply exclusively for orders placed with Siemens Aktiengesellschaft, Germany.

# 1.1 For customers with a seat or registered office in Germany

For customers with a seat or registered office in Germany, the following terms and conditions apply subordinate to T&C:

- for products, which include specific terms and conditions in the description text, these specific terms and conditions shall apply and subordinate thereto,
- for installation work the "General Conditions for Erection Works – Germany"<sup>1)</sup> ("Allgemeine Montagebedingungen – Deutschland" (currently only available in German)) and/or
- for stand-alone software products and software products forming a part of a product or project, the "General License Conditions for Software Products for Automation and Drives for Customers with a Seat or registered Office in Germany"<sup>1</sup>) and/or
- for consulting services the "General Terms and Conditions for Consulting Services of the Division DF – Germany"<sup>1)</sup> and/or
- for other supplies and/or services the "General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry"<sup>1</sup>).

In case such supplies and/or services should contain Open Source Software, the conditions of which shall prevail over the "General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry"<sup>1</sup>), a notice will be contained in the scope of delivery in which the applicable conditions for Open Source Software are specified. This shall apply mutatis mutandis for notices referring to other third party software components.

# 1.2 For customers with a seat or registered office outside Germany

For customers with a seat or registered office outside Germany, the following terms and conditions apply subordinate to T&C:

- for products, which include specific terms and conditions in the description text, these specific terms and conditions shall apply and subordinate thereto,
- for services the "International Terms & Conditions for Services"<sup>1)</sup> supplemented by "Software Licensing Conditions"<sup>1)</sup> and/or
- for consulting services the "General Terms and Conditions for Consulting Services of the Division DF – Germany"<sup>1</sup>) and/or
- for other supplies of hard- and software the "International Terms & Conditions for Products"<sup>1</sup>) supplemented by "Software Licensing Conditions"<sup>1</sup>)

#### 1.3 For customers with master or framework agreement

To the extent our supplies and/or services offered are covered by an existing master or framework agreement, the terms and conditions of that agreement shall apply instead of T&C.

### 2. Prices

The prices are in  ${\ensuremath{\in}}$  (Euro) ex point of delivery, exclusive of packaging.

The sales tax (value added tax) is not included in the prices. It shall be charged separately at the respective rate according to the applicable statutory legal regulations.

Prices are subject to change without prior notice. We will charge the prices valid at the time of delivery.

To compensate for variations in the price of raw materials (e.g. silver, copper, aluminum, lead, gold, dysprosium and neodym), surcharges are calculated on a daily basis using the so-called metal factor for products containing these raw materials. A surcharge for the respective raw material is calculated as a supplement to the price of a product if the basic official price of the raw material in question is exceeded.

The metal factor of a product indicates the basic official price (for those raw materials concerned) as of which the surcharges on the price of the product are applied, and with what method of calculation.

An exact explanation of the metal factor can be downloaded at:

#### www.siemens.com/automation/salesmaterial-

#### as/catalog/en/terms\_of\_trade\_en.pdf

To calculate the surcharge (except in the cases of dysprosium and neodym), the official price from the day prior to that on which the order was received or the release order was effected is used.

To calculate the surcharge applicable to dysprosium and neodym ("rare earths"), the corresponding three-month basic average price in the quarter prior to that in which the order was received or the release order was effected is used with a onemonth buffer (details on the calculation can be found in the explanation of the metal factor).

#### 3. Additional Terms and Conditions

The dimensions are in mm. In Germany, according to the German law on units in measuring technology, data in inches apply only to devices for export.

Illustrations are not binding.

Insofar as there are no remarks on the individual pages of this catalog – especially with regard to data, dimensions and weights given – these are subject to change without prior notice.

 The text of the Terms and Conditions of Siemens AG can be downloaded at www.siemens.com/automation/salesmaterial-as/catalog/en/ terms\_of\_trade\_en.pdf

### 4. Export Regulations

We shall not be obligated to fulfill any agreement if such fulfillment is prevented by any impediments arising out of national or international foreign trade or customs requirements or any embargoes and/or other sanctions.

Export may be subject to license. We shall indicate in the delivery details whether licenses are required under German, European and US export lists.

Our products are controlled by the U.S. Government (when labeled with "ECCN" unequal "N") and authorized for export only to the country of ultimate destination for use by the ultimate consignee or end-user(s) herein identified. They may not be resold, transferred, or otherwise disposed of, to any other country or to any person other than the authorized ultimate consignee or end-user(s), either in their original form or after being incorporated into other items, without first obtaining approval from the U.S. Government or as otherwise authorized by U.S. law and regulations.

The export indications can be viewed in advance in the description of the respective goods on the Industry Mall, our online catalog system. Only the export labels "AL" and "ECCN" indicated on order confirmations, delivery notes and invoices are authoritative.

Products labeled with "AL" unequal "N" are subject to European / national export authorization. Products without label, with label "AL:N" / "ECCN:N", or label "AL:9X9999" / "ECCN: 9X9999" may require authorization from responsible authorities depending on the final end-use, or the destination. If you transfer goods (hardware and/or software and/or technology as well as corresponding documentation, regardless of the mode of provision) delivered by us or works and services (including all kinds of technical support) performed by us to a third party worldwide, you must comply with all applicable national and international (re-)export control regulations.

If required for the purpose of conducting export control checks, you (upon request by us) shall promptly provide us with all information pertaining to the particular end customer, final disposition and intended use of goods delivered by us respectively works and services provided by us, as well as to any export control restrictions existing in this relation.

The products listed in this catalog may be subject to European/German and/or US export regulations. Any export requiring approval is therefore subject to authorization by the relevant authorities.

Errors excepted and subject to change without prior notice.


© Siemens 2019

# Appendix

### Selection and ordering at Siemens

Industry Mall, Catalog CA 01, downloading and ordering catalogs

#### Easy product selection and ordering: Industry Mall and Interactive Catalog CA 01





Products for automation and driver Regardless of whether you are intere large drives, automation systems or is system; with the interactive Catalog end existy, and easily search through extension portfolio of Siemens Indust Automation and Dhine's Technologies, contains information on our products, and solutions as well as a variety of a

> New every October: DVD with information on more than 100,000 products. The CA 01-0VD combines the clarity of a catalog with the instart updates of the letterut. An interface to the online ordering system makes the purchasing process even more conveniet. So you can obtain information and make up orders in the CA 01 Catalog, and the check the analability of the selected products and track your orders in the online ordering system.



#### Downloading catalogs


General Inf

> Catalog update

Regional ve Support

> Frequently As

ha Catalog CA 01 O



#### Ordering printed catalogs



#### Industry Mall

The Industry Mall is a Siemens AG Internet ordering platform. It provides you with online access to a comprehensive product spectrum that is presented in an informative, well-organized way.

Powerful search functions help you select the required products, while configurators enable you to configure complex product and system components quickly and easily. CAx data are also available for you to use.

Data transfer allows the entire procedure, from selection through ordering to tracking and tracing, to be carried out online. Availability checks, individual customer discounting, and quotation preparation are also possible.

www.siemens.com/industrymall

#### Interactive Catalog CA 01 - Products for automation and drives

The Interactive Catalog CA 01 combined with the Siemens Industry Mall unites the benefits of offline and online media in one application – the performance of an offline catalog with the availability of a wide range of up-to-date information on the Internet.

Select products and assemble orders using the CA 01, determine the availability of the selected products, and track and trace them via the Industry Mall.

Information and download: www.siemens.com/automation/ca01

#### Siemens Industry Online Support

You can download catalogs and brochures in PDF format from Siemens Industry Online Support without having to register.

The filter box makes it possible to perform targeted searches.

www.siemens.com/industry-catalogs

Please contact your local Siemens branch if you are interested in ordering printed catalogs. Addresses can be found at www.siemens.com/automation-contact Digital Industries Process Automation Östliche Rheinbrückenstr. 50 76187 Karlsruhe, Germany

Published by Siemens

PDF (E86060-D4001-A510-D8) KG 0719 276 En © Siemens 2019

Availability and technical specifications are subject to change without notice. The information provided in this catalog contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.

All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.

# Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, systems, machines and networks.

In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial security concept. Siemens' products and solutions constitute one element of such a concept.

Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place.

For additional information on industrial security measures that may be implemented, please visit https://www.siemens.com/industrialsecurity.

Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats.

To stay informed about product updates, subscribe to the Siemens Industrial Security RSS Feed under https://www.siemens.com/industrialsecurity.