

SITOP PSU8600 – A new basic 4 x 5 A device enables the power supply system's unique functions, including in single-phase networks – see page 6/7 and technical data on page 20.



SITOP PSU6200 – the all-around power supply for a wide range of applications, now also for deployment in hazardous areas – see page 8/9 and technical data on page 26/27.





SITOP power supplies bring production plants to life.

An efficient power supply is a basic requirement for operating any plant, no matter the industry or need. Critical production processes can only be maintained if a constant power supply of the necessary quality is available for the automation system. For decades, SITOP – the heart of automation – has been bringing production plants to life. The complete, precisely coordinated range of products guarantees a reliable power supply, and is especially suited to the growing demands of our time.



SITOP means top reliability

SITOP has proven its reliability in nearly all networks around the world. With a flexible, wide-range input, outstanding load characteristics, and all the relevant certifications, SITOP power supply units safeguard the availability of your plant. Add-on modules prevent problems on the line or DC side. And when upgraded to an uninterruptible power supply, the 24-V power supply units bridge power failures for a period of seconds, minutes, or hours. In the event of a fault-specific overload or short circuit in the output circuit, selective disconnection of

the feeder ensures continued operation, because the supply to other loads is maintained. For highly critical applications, redundant power supply solutions are also an option. If a replacement is ever needed, our global customer service ensures the fastest possible delivery: All SITOP products can be supplied from stock.



SITOP means top efficiency

Reduced energy costs are a valuable competitive advantage. SITOP makes an important contribution, because the primary switched-mode power supply units operate highly efficiently. For example, SITOP PSU8200 and 6200 have an efficiency of up to 96 percent. Losses are low throughout the entire load range, even in no-load operation. This is because a power supply is rarely operated at full load. SITOP PSU8600, on the other hand, records power data from all outputs, which is then further processed in energy management systems. And via PROFlenergy, power supply outputs can be switched off selectively: for example, during breaks.

Efficiency also characterizes the product lifecycle. With the TIA Selection Tool, we offer you special tools to make it easy to select a power supply and DC UPS. We provide you with all the design data for all common CAE systems as well as the corresponding product documentation.



SITOP is top in integration

SITOP sets a benchmark in terms of integration: Complete integration of the SITOP PSU8600 power supply system and SITOP UPS1600 DC UPS in Totally Integrated Automation, the TIA Portal, and the new SITOP Manager saves time and money and facilitates fail-safe engineering. For the selectivity modules and the SITOP PSU6200 product line, S7 function blocks evaluate important diagnostic information. The SITOP UPS1600 can easily be integrated via USB or Ethernet to protect PC-based automation systems from power failures. And the SITOP library for SIMATIC PCS 7

enables a transparent 24-V supply in the process control system during ongoing operation.

Besides PROFINET, SITOP PSU8600 and SITOP UPS1600 also communicate via OPC UA. With the OPC UA server, it's also possible to directly integrate units such as controllers or PCs into automation applications with OPC UA clients from different vendors.

Three SITOP categories for the different demands on an industrial power supply

Advanced power supplies

The switched-mode power supply units in the Advanced performance class are the optimal choice for maximum reliability and functionality as required in the process and automotive industries, in special-purpose machine manufacturing, and in harsh environments. The SITOP PSU8200 product line meets these extreme requirements thanks, for example, to their overload behavior, efficiency, and compactness. SITOP PSU8600 also offers a power supply system with open communication for optimal integration into the digital environment.

Standard power supplies

Our standard portfolio was designed for industrial applications like those in special-purpose machine manufacturing. Development of the new SITOP PSU6200 all-around power supply was based on our experience with the proven SITOP smart product line. This new SITOP standard power supply features even higher efficiency, comprehensive diagnostic options, and greater ruggedness.

Basic power supplies

From flat power supplies for distribution boards to costeffective basic power supplies and slim power supply units for control boxes – even in the low-performance range, SITOP leaves nothing to be desired. LOGO!Power offers you miniature power supply units in the LOGO!8 module design. And SITOP lite meets the most mportant requirements for reliable primary switched-mode regulators at an affordable price.

Overview of SITOP product lines

Advanced power supplies



SITOP PSU8600

The power supply system for digitalization and Industry 4.0

The innovative SITOP PSU8600 power supply system is fully integrated into Totally Integrated Automation and the TIA Portal. It's integrated directly into networked automation applications via its Ethernet/PROFINET interface or OPC UA. SITOP PSU8600 offers unique functions and diagnostics options. The modular system can be expanded to 36 outputs and provides buffer and DC UPS modules for protection against power failures.

Pages 20-23



SITOP PSU8200

The technology power supply for demanding solutions

SITOP PSU8200 is ideal for complex plants and machines. The wide-range input allows it to be connected to any supply system and also to withstand large voltage fluctuations. The power boost briefly delivers up to three times the rated current. And in the event of an overload, you can choose between constant current with automatic restart or latching shutdown. The high degree of efficiency reduces energy consumption, while the compact metal enclosure saves space.

Pages 24-25

What an optimal power supply looks like depends on numerous factors – size, performance range, and functions, to name but a few. The extensive range of SITOP products ensures that your power supply will always match your requirements.

Standard power supplies





SITOP PSU6200

The all-around power supply for a wide range of applications

SITOP PSU6200 is the extremely highperformance power supply for standard 24-, 12-, and 48-V applications. The compact and energy-efficient power supply units offer comprehensive functions and features for focused diagnostics, fast installation, and dependable operation. Whether it's LED status indicators, integration into preventive maintenance, push-in terminals, or rugged input – SITOP PSU6200 has it all.

Pages 26-27



SITOP smart

The powerful standard power supply

SITOP smart is the optimal power supply for many 24-V and 12-V applications, featuring powerful performance and an affordable price. Even large loads can be easily switched on, thanks to its overload characteristics that provide 1.5 times the rated current for 5 seconds. And with a rated capacity of 120 percent at ambient temperatures up to 45°C, these slim power supply units are among the most reliable of their kind.

Pages 28-29

Basic power supplies

SITOP DC/DC converters

SIMATIC Design



SITOP lite

The cost-effective basic power supply

SITOP lite is the power supply series for basic requirements in the industrial environment, offering all the important functions at a low cost – without compromising quality and reliability. The widerange input with manual switchover supports connection to a wide range of single-phase supply systems.

Page 32



LOGO!Power

The flat power supply for distribution boards

Small. Clever. LOGO!Power. The fourth generation of the globally proven miniature power supply units with a flat, stepped profile features high performance in a small space. The comprehensive functionality with flexible installation, current monitoring, and high energy efficiency permits universal use in applications with 5 V, 12 V, 15 V, and 24 V.

Pages 30-31



SITOP DC/DC converter

Stable power supply despite fluctuating DC voltage

SITOP DC/DC converters provide a stable control voltage: in battery-powered vehicles, as a "refresher" on long lines, in power plants, and at the DC link converter of wind energy plants and machine tools.

Page 34–35

The optimal supply for SIMATIC S7 and more

Page 33

Special designs


Equipped for special functions and conditions

Pages 36-37

SITOP PSU8600 – the power supply system for digitalization and Industry 4.0

Complex plants set high requirements for the efficiency, flexibility and reliability of the components used. The innovative power supply system SITOP PSU8600 fulfills them all – thanks to its unique functionality, diagnostics capability, modular expandability and complete integration in TIA or via an OPC-UA server in many other systems.

Advanced power supplies




SITOP PSU8600 – in dialog with your power supply

The SITOP power supply system includes the SITOP PSU8600 basic unit, the SITOP CNX8600 add-on modules, the SITOP BUF8600 buffer modules and the SITOP UPS8600 UPS module with the BAT8600 battery modules. It can be integrated seamlessly in TIA Portal, SIMATIC PCS 7 and WinCC. Due to the comprehensive data exchange over PROFINET or OPC-UA, the power supply is in constant dialog with the control unit and thus enables preventive maintenance and energy management in the control and load circuit.

Did you know that...

even in buffer operation, the outputs exactly hold their set voltage and do not vary with battery voltage, as is common in other DC UPS systems?



The modular system toolbox



Base unit

Power supply 24 V/20 A or 40 A with one or four selectively monitored outputs

Expansion modules

Expansion to up to 36 selectively monitored outputs

Buffer modules

Bridging short power failures

DC UPS and battery modules

Bridging long power failures



Fast and easy integration in the automation

The SITOP PSU8600 power supply system can be integrated seamlessly in TIA portal, SIMATIC PCS 7 and WinCC. Two industrial PROFINET/ethernet ports enable the system to be integrated easily into the automation environment. Thanks to the open communication interface OPC UA, vendor-independent data exchange is possible.

The parameterization, operation and monitoring for this can take place via the user-friendly engineering and diagnostics software SITOP Manager. The integrated web server enables remote access. Due to the support of PROFlenergy, outputs can be switched off specifically and thus save energy and costs during break periods.



High degree of flexibility thanks to modular system unit

The compact basic unit provides one or four individually adjustable outputs – and thus up to four power supplies in one device. Each output can be set flexibly to 4–28 V, even dynamically during operation and with selective monitoring for overcurrent. The "system clip link" can be used to extend the power supply system with various modules without additional wiring work and therefore expand it to up to 36 outputs and provide protection against supply system outages.



High plant availability

The comprehensive diagnostics options of the SITOP PSU8600 power supply system provide the basis for preventive maintenance. Faults can therefore be detected, assigned and corrected in the shortest possible time. To ensure that a short-circuit or an overload in a single load does not lead bring the entire plant to a standstill. All outputs, whose voltage and current threshold can be set individually, are monitored selectively and in the event of a fault, are switched off individually. Because the current of each output can be recorded continuously and transmitted via PROFINET, overload states can be detected early. With the suitable buffer and battery modules, supply system failures can be bridged from seconds to hours, thus preventing a plant standstill.

SITOP PSU6200 – the all-around power supply for a wide range of applications

A new benchmark in the area of standard power supplies: With its award-winning industrial design, space-saving width, optimized terminals, comprehensive diagnostics options, and high operational reliability, SITOP PSU6200 offers attractive prospects for a variety of different applications and areas of operations.

Standard power supplies







Focused diagnostics. Top integration.


With SITOP PSU6200 you benefit from a high degree of transparency during operation. Thanks to the integrated diagnostics monitor, in the more powerful units, an LED display on the housing enables immediate identification of how high the power supply's load is or whether the unit is coming to the end of its life. In this way it is possible to respond to critical states to prevent unforeseen plant failure.


Via the power supply unit's diagnostics interface, additional important operating parameters and statuses such as current, voltage, overload, operating hours, temperature, and device/type can be transferred to the controller and incorporated in condition monitoring. The signal is evaluated by means of a free S7 function block. In addition, a faceplate for visualizing the data on an HMI is available for download.

Did you know that only one digital input is required on the PLC for transferring comprehensive diagnoses?


Diagnostics monitor/Diagnostics interface

SITOP PSU6200 power supply units as of 24 V/10 A, 12 V/12 A and 48 V/5 A have a diagnostics monitor and a diagnostics interface. The diagnostics monitor indicates their operating status, current utilization, and end of service life via 5 LEDs.





The diagnostics interface outputs a serial code to a digital input of a PLC that is evaluated by a function block. A WinCC faceplate makes visualization easy:









Fast installation. Top efficiency.

Space savings, front labeling, push-in terminals – with SITOP PSU6200, you make no compromises when installing and wiring. Inside the control cabinet, space is a valuable commodity. You can make even better use of this space, thanks to the extremely narrow width of the new power supply units. And thanks to optimized heat dissipation and an efficiency rate up to 96 percent, the units require no lateral clearance between components, which also saves space on the DIN rail.

The all-around power supplies also facilitate and speed up fail-safe wiring. Unique terminal labeling makes correct wire connection easier, and push-in terminals make wiring fast. An additional, uniquely identified minus terminal also makes it easier to ground PELV (protective extra-low voltage) circuits according to the Machinery Directive.



Dependable operation. Top reliability.

Dependable overload behavior, robust input, and a metal enclosure for optimal heat dissipation – with SITOP PSU6200, you're on the safe side. Their extra power means that the highperformance power supply units provide a 50 percent higher rated current for up to five seconds in the event of an overload. If the overload is extremely high, they keep the current constant and change to hiccup mode for self-protection only when the output voltage drops to 15 volts. Once the verload has been corrected, they continue in normal operation.

You're also optimally equipped to handle bad line quality. Thanks to the robust wide-range input for AC and DC voltage, these all-around power supplies are well-protected against undervoltages and overvoltages from the grid. In the event of a phase failure, the 400-V units even permit continuous twophase operation. The higher-performance power supply units also have active power factor correction (PFC) that keeps the reactive current and inrush current low.

New redundancy, buffer, and selectivity modules in the attractive SITOP PSU6200 design ensure even higher availability. See pages 12 and 13.



SITOP ensures reliable 24-V supply – even when the power fails

Power outages can bring a plant to a standstill, with high costs in terms of both time and money. The SITOP DC UPS systems with different types of energy storage devices and communication interfaces offer solutions for all buffering time and plant integration requirements.

Uninterruptible power supply



DC UPS module

For expansion to an uninterruptible 24-V power supply

DC UPS module
For expansion to an uninterruptible
24-V power supply





SITOP DC UPS with battery modules

Compact DC UPS modules ensure continued operation, even over a period of hours, depending on battery capacity and power requirements.

High system availability thanks to battery management

Sophisticated battery management ensures optimal battery charging. The charging process is temperature-controlled thanks to the innovative SITOP UPS1600, which also increases the service life of the UPS1100 battery module.

- DC PSU module SITOP UPS1600 with 24 V and up to 40 A as well as battery module UPS1100 up to 12 Ah (total 72 Ah)
- SITOP UPS1100 5-Ah lithium battery module (LiFePo) with a constant power output and voltage throughout the discharging range as well as a long service life even with high ambient temperatures
- Monitoring of operational readiness, battery feeder, and charging status
- Extended battery life thanks to battery management



SITOP DC UPS with capacitors

These high-capacitance double-layer capacitors (Ultracaps) store sufficient energy to shut down PC-based systems safely.

Totally maintenance-free

The capacitors have an extremely long life even at high ambient temperatures. No maintenance or replacement of the energy buffer is required, which means that the DC UPS pays for itself within a short time. And because the capacitors do not emit any gas, no ventilation of the control cabinet is required. Short recharging times quickly restore buffering capability following a power failure.

For use both inside and outside the control cabinet

The buffering time of the UPS500S for DIN rail mounting can be extended by adding UPS501S expansion modules.

- Variant expandable up to 20 kWs for longer buffering times
- Capacitors eliminate replacement of batteries
- Long life even at high temperatures
- No ventilation of the installation site required
- Communication via contacts or USB
- Easy engineering via SITOP Manager (as of V1.1, see page 16 for more details)

Did you know that ... you can connect the uninterruptible power supply SITOP UPS1600 to various different systems via OPC UA?

SITOP module for 24-V buffering	Buffer module	UPS500	UPS	1600
Energy storage device				
Buffer time up to	Second	Minutes	Но	urs
Storage medium	Electrolytic capacitors	Double-layer capacitors	Lead batteries	Lithium batteries
Service life (also temperature-dependent)	++	++	•	+
Application area (temperature, ventilation)	+	+	•	+
UPS module/electronics				
max. rated output current	40 A	15 A	40) A
Overload capacity	++	+	4	++
Interfaces		I/O, serial, USB	I/O, USB, Ethernet/PROFINET	
Operating and diagnostic information via				
– Signaling contacts		•		•
- OPC UA server, Web server, S7 FBs, WinCC faceplate				•
Shutting down multiple PCs/PLCs				•
Start from battery without mains voltage (island operation)				•
Engineering via SITOP Manager		•		•
Engineering via TIA Portal, STEP 7, WinCC, or OPC UA				•
SITOP library for SIMATIC PCS 7				•


Extremely communicative

Optional communication via USB or Industrial Ethernet/ PROFINET. With open communication via Ethernet, configuration and diagnostics are conveniently performed by the SITOP Manager. This PC software with a user interface based on a Web browser permits simple parameterization: for example, for safely shutting down multiple PCs.

The UPS1600 can even be fully integrated into TIA via PROFINET. Remote monitoring is possible with support from the integrated web server.


- Communication via contacts, USB, or two Ethernet/ **PROFINET** ports
- Easy engineering and extensive diagnostics in the TIA Portal
- OPC UA server for the flexible integration of a wide variety of automation, operating, and monitoring systems
- User-friendly SITOP Manager engineering and diagnostics tool for simple integration into open systems (more details on page 16)

SITOP DC UPS configuration with capacitors



24-V buffering for saving process data and for correct PC shutdown

SITOP DC UPS configuration with battery modules



24-V buffering for maintaining communications, signaling, sensor-measured values, and position values

SITOP add-on modules – all-round protection à la carte

Processes and plants that are critical for a company's business generally require additional protection measures. SITOP add-on modules individually protect your production against many sources of risk.

Add-on-Module



Add-on modules

For increasing system availability to all-round protection



Safeguarding against failure through redundancy

Two power supply units can be connected via the SITOP redundancy module for additional failure safety. If one unit fails, the other automatically takes over the power supply function. Even in the event of a short circuit inside a power supply unit, the power supply remains reliable. Thanks to its high dielectric strength, the new RED1200 redundancy module also decouples power supplies without output voltages up to 48 V.



Selective disconnection of faulty 24-V feeders

The SITOP selectivity modules are specifically tailored to switched-mode power supplies. The modules permit brief current peaks and switch off the electricity for longer overloads, even on long, thin cables and with creeping short circuits in which the current is limited by the high ohmic resistance. In this case the circuit-breakers do not trip, or they trip too late, even if the power supply could deliver the current. The selectivity modules reliably disconnect the faulty load circuits, and the supply to the other loads continues with absolutely no interruption so that total failure of the plant can be avoided. The affected feeder is indicated by an LED. The option with single-channel signaling also allows remote output-specific fault location. The new SEL1200 and SEL1400 four or eight-channel modules also have an interface with comprehensive diagnostics options for each output.


Selection matrix of the SITOP add-on modules for protection from	Redundany	Selectivity oliagnosticity	Buter "nodu,	OCUPS GPBGGOWITH	OCUPS With batteries
Failure of a power supply unit	•				
Overload in the 24-V circuit		•			
Power failure up to the seconds range			•	•	•
Power failure up to the minutes range				•	•
Power failure up to the hours range					•





Buffer module bridges brief power failures

Although power failures usually last only a fraction of a second, they can cause costly and time-consuming damage. In combination with the 24-V power supply units, the buffer module bridges short-duration voltage dips with its electrolyte capacitors.

Did you know that ... our customers use SITOP power supply units in manufacturing, process, and building automation in over 190 countries worldwide?







Your benefits with the redundancy module:

- Highly secure DC supply thanks to a redundant design
- Reliable supply even when one power supply fails
- Compact redundancy modules for power supply units up to 48 V and 40 A
- 24-V/NEC Class 2 redundancy module limited to 100 VA
- Decoupling of parallel-connected power supply units to enhance performance or of series-connected power supply units to increase voltage

Your benefits with the selectivity module:

- Protection against overloads and short circuits in the 24-V circuit
- Reliable tripping, regardless of the line resistance
- SEL1200: switch-off characteristic for standard protection and high starting currents
- SEL1400/PSE200U: power limiting to meet high protection requirements by stabilizing the 24 V
- Sequential connection reduces total inrush current
- Common signaling contact or evaluation of individual channels
- SEL1200/1400: 4 or 8 outputs, each with diagnostics of voltage, current, set threshold, reason for disconnection (if applicable)
- PSE200U: 4 outputs with voltage measuring point for current (1 V \triangleq 1 A)

Your benefits with the buffer module:

- Inexpensive protection against power failure up to several seconds
- Support of power supply unit for temporarily increased power requirements
- High load current up to 40 A
- Connection to the power supply unit only via two lines

Comprehensive support from planning to operation



CAD and CAE data in the image database for simple configuration

All product information is available per download via the CAx download manager.


No matter how many requirements a power supply must meet, SITOP always optimally supports your planning process – from product selection and mechanical and electrical design to project-specific plant documentation and engineering. With the TIA Selection Tool, you can select your power supply, add-on modules, and DC UPS faster and order it directly. In addition, you will automatically receive the required CAD data and circuit diagram macros. And using the TIA portal, you can even simply and reliably parameterize and diagnose the modular SITOP UPS8600 power supply system and the SITOP UPS1600 DC uninterruptible power supply.

Efficiency starts with selection


With just a few mouse clicks, the TIA Selection Tool guides you to the optimal power supply for your requirements. Simply enter the relevant parameters. If there are multiple solutions, an overview offers a comparison table containing several devices. Once you've opted for a power supply, you can easily select the appropriate redundancy, selectivity, and DC UPS modules. You can then export the resulting product configuration to various CAD, CAE, and engineering systems (like the TIA Portal) and continue to use it. With a single mouse click, you can transfer the selected products to the Industry Mall shopping cart and conveniently order them from there. The 24-V consumer view in the TIA Selection Tool helps you easily select the power supply for your project by automatically calculating the power requirements of the automation products to be supplied.

Everything you need for planning

Additional information – including 3D data, circuit diagram macros according to IEC or ANSI, certificates, and operating instructions – are available at the click of a mouse. With the aid of the CAx Manager, you can download engineering data in the DXF, STEP, EPLAN, and eCl@ss advanced formats and apply it directly to your project engineering. Not only does this save you a significant amount of valuable engineering time, but you also benefit from the configurable manuals when creating custom project documentation using My Documentation Manager.



TIA Selection Tool: In the 24-V DC power consumer view, the necessary SITOP power supply can be easily selected for the chosen automation products.



TIA Selection Tool: Power supply selection based on technical specifications


Did you know that... SITOP PSU8600 and SITOP UPS1600 (version with IE/PN interface) have integrated Web servers that they can use for commissioning and remote diagnostics?

Convenient engineering in the TIA Portal


You can easily perform the engineering tasks for the SITOP PSU8600 power supply system and the SITOP UPS1600 uninterruptible power supply via the TIA Portal. Device selection and network connection are a simple matter of dragand-drop or copy-and-paste. In addition, function blocks for SIMATIC S7-300, 400, 1200, and 1500 are available for integrating the power supply system and DC UPS into STEP 7 user programs. There are also tailor-made faceplates to visualize the operational and diagnostic data using SIMATIC operating and monitoring systems. All of this helps reduce engineering effort and saves costs.

Your advantages through system integration of SITOP UPS1600 and SITOP PSU8600

- Time and cost savings during configuration and operation
- Convenient engineering in the TIA portal
- Quick product selection and network integration in PROFINET
- Comprehensive parameterization of devices
- Comprehensive diagnostic options
- Simple integration into STEP 7 user programs with function blocks for \$7-300/400/1200/1500
- Fast integration into operation and monitoring with faceplates for SIMATIC panels and SIMATIC WinCC



Integrating the SITOP UPS1600 DC UPS into PROFINET is easy and fail-safe via the TIA Portal.



Configuring and setting parameters for the PSU8600 power supply system in the TIA Portal is both intuitive and convenient.



siemens.com/ tia-selection-tool

SITOP Manager – the software for easy integration of SITOP PSU8600, UPS500, and UPS1600 in open systems



Did you know that ... with the new SITOP Manager V1.1, you can configure and diagnose uninterruptible SITOP power supplies with a USB interface, which also includes SITOP UPS500 and predecessors of UPS1600?

Optimal interoperability with different control systems: SITOP Manager – the Windows software for the SITOP PSU8600 power supply system and SITOP uninterruptible power supplies – is available free of charge.

High performance for configuration

With the SITOP Manager software, all the power supplies in a network can be parameterized and diagnosed by a PC with the Windows 7 or 10 operating system. This is ideal, especially if plant configuration and programming isn't performed via the TIA Portal or SIMATIC Step 7. Thanks to a user interface based on a Web browser, the application can also run on mobile terminals and automatically adapts the display size.

With the user-friendly SITOP Manager software, it's easy to parameterize the SITOP PSU8600 power supply system and the SITOP uninterruptible power supplies – for example, to define output voltages and current thresholds or to safely shut down PCs in the event of a power failure.

Uncompromising when it comes to security

Communication between SITOP Manager and the connected power supplies is via the open, multi-vendor, Ethernet-based OPC UA communication standard. This standard meets extremely high security requirements for secure data transmission.



The status of the communication-capable SITOP devices can be conveniently obtained via online diagnostics in the SITOP Manager. Here is the operating data for the SITOP UPS1600/UPS1100.

SITOP – the right power supply for every application

		Advanced po	ower supplies	Standard po	wer supplies	Basic power supplies		
			SITOP PSU8600 – power supply system with PROFINET and OPC UA	SITOP PSU8200 – The technology power supply for demanding solutions	SITOP PSU6200 – the all-around power supply for a wide range of applications	SITOP smart – The powerful standard power supply	SITOP lite – The costeffec- tive basic power supply	LOGO!Power – The flat power supply for distribution boards
	ix of the SITOP DII cording to perfor unctions	•						
Input/output	Input	AC/DC	1,3 ~	1,2,3 ~ =	1,3 ~ =	1,3 \sim	1 \sim	1 ~ =
	Rated power up to approx.	Р	960 W	960 W	480 W	960 W	480 W	100 W
→ ~= →	Rated output voltages	U	5–24 V DC	24/36/48 V DC	12/24/48 V DC	12/24 V DC	24 V DC	5/12/15/24 V DC
	Rated output currents (24 V)	1	20-40 A	5–40 A	1.3–20 A	2.5–40 A	2.5–20 A	0.6-4.0 A
Properties	Overload behavior	P _{max}	Extra Power	Extra Power Power Boost	Extra Power	Extra Power		Extra power on startup
	Energy efficiency		+++ PROFenergy	+ + +	+ + +	+ +	+	+ +
	Automation integration		epopu" There SPC UA	—— DC o.k. Remote on/off	DC o.k. Diagnostics interface	—— DC o.k.		
Safety, environment	Explosion protection: ATEX, IECEx, CCC, or FM	$\langle \xi_{\rm X} \rangle$	•	•	•	•		•
	Marine approval: DNV GL or ABS	<u> </u>	•	•	in preparation	•		•
	Ambient temperature range		−25 +60 °C	−25 +70 °C	−30 +70 °C	−25 +70 °C	0 +60 °C	−25 +70 °C
24-V power supply units	Redundancy module	 	•	•	•	•	•	•
expandable with	Selectivity module	-G 1>	integrated	•	•	•	•	•
3	Buffer module		integrated	•	•	•	•	•
	DC UPS with Ultracaps	min	integrated	•	•	•	•	•
	DC UPS with batteries	- <u>+</u> h	integrated	•	•	•	•	•

Our answers to your requirements with regard to a highperformance power supply:

The selection of the power supply unit is based on the input and output data. On the following two pages (pages 18 and 19), you will find a selection table with the available SITOP power supply units and the product lines to which they belong. The technical data is located on the subsequent pages under the corresponding product line.

But which product line is the right one for my application?

As a decision-making aid, you can refer to the selection matrix containing the most important data, properties, functions, certificates, and expansion options for increasing 24-V availability.

Selection table SITOP power supplies

Input voltage	Output	Advanced po	ower supplies	Standard po	wer supplies		Basic power supplie	s	SIMATIC design	SITOP DC/DC converter
	current	SITOP PSU8600	SITOP PSU8200	SITOP PSU6200	SITOP smart	SITOP lite	LOGO!Power	SITOP compact		
DC 24-V output v	voltage		5.1.5.1.555255	3.101.10020	J. C. S. a.	5.757	2000	Jiror compact		
1-phase	0.6 A						6EP3330-6SB00-0AY0	6FP1331-5RΔ00		
120 V, 230 V AC				6EP3331-7SB00-0AX0			6EP3331-6SB00-0AY0			
120 1, 250 1 7.0	2 A			021333173800 0///0			0213331 03800 07110	OLI 1331 3B/(10	6ES7307-1BA01-0AA0	
	2.5 A			6EP3332-7SB00-0AX0	6EP1332-2BA20	6EP1332-1LB00	6EP3332-6SB00-0AY0	6EP1332-5BA00	6EP1332-1SH71	
	3 A								6EP1332-4BA00	
	3.5 A								6EP1332-1SH31	
	3.7 A			6EP3333-7LB00-0AX0				6EP1332-5BA20		
	4 A						6EP3333-6SB00-0AY0	6EP1332-5BA10		
	5 A		6EP1333-3BA10	6EP3333-7SB00-0AX0	6EP1333-2BA20	6EP1333-1LB00			6ES7307-1EA01-0AA0	
			6EP3333-8SB00-0AY0						6ES7307-1EA80-0AA0	
									6EP7133-6AB00-0BN0	
	6.2 A									
	8 A		(FR4224 2R440	(FD2224 70000 24V0	(FR4224 2R422	CER422441800			6EP1333-4BA00	
	10 A		6EP1334-3BA10	6EP3334-7SB00-3AX0		6EP1334-1LB00			6ES7307-1KA02-0AA0	
	12.5 A		6EP3334-8SB00-0AY0		6EP1334-2AA01-0AB0				6EP7133-6AE00-0BN0	
	20 A		6EP1336-3BA10	6EP3336-7SB00-3AX0	6ED1336-2RA10	6EP1336-1LB00				
		6EP3336-8MB00-2CY0	0L1 1330-3BA10	0LI 3330-73B00-3AX0	0L11330-2DA10	0L11330-1LB00				
	40 A	OLI 3330 OMBOO ZCIO	6EP3337-8SB00-0AY0							
3-phase	5 A		6EP1333-3BA10 ¹⁾	6EP3433-7SB00-0AX0	6EP1433-2BA20					
	8 A								6ES7148-4PC00-0HA0	
	10 A		6EP1334-3BA10 ¹⁾	6EP3434-7SB00-3AX0	6EP1434-2BA20					
	17A									
	20 A		6EP3436-8SB00-0AY0	6EP3436-7SB00-3AX0	6EP1436-2BA10					
		6EP3436-8SB00-2AY0								
	20 A/	6EP3436-8MB00-2CY0								
	4 x 5 A	0213130 0MB00 2C10								
	30 A									
	40 A	CER2427 OCROO 24VO	6EP3437-8SB00-0AY0		6EP1437-2BA20					
	40 A/	6EP3437-8SB00-2AY0								
	4 x 10 A	6EP3437-8MB00-2CY0								
12 V DC	4 X 10 A									6EP3133-0TA10-0AY0
24-110 V DC	2 A								6ES7305-1BA80-0AA0	52.5.55 67.116 67.116
24 V DC	5 A									6EP3133-0TA00-0AY0
	10 A									6EP3134-0TA00-0AY0
	3,5 A									6EP3233-0TA10-0AY0
48 V DC	5 A									6EP3233-0TA00-0AY0
	10 A									6EP3234-0TA00-0AY0
	0.6 A						6EP3330-6SB00-0AY0			
	1.3 A			6EP3331-7SB00-0AX0			6EP3331-6SB00-0AY0			
110 2001/20	2.5 A			6EP3332-7SB00-0AX0			6EP3332-6SB00-0AY0			
110-300 V DC	3.7 A			6EP3333-7LB00-0AX0			6ED2222 6CD00 04V0	6EP1332-5BA20		
120-240 V DC	4 A 5 A			6EP3333-7SB00-0AX0			6EP3333-6SB00-0AY0	DEP (33Z-5BATU		
	5 A 10 A			6EP3333-7SB00-0AX0						
	20 A			6EP3336-7SB00-3AX0						
110-220 V DC		6EP3336-8MB00-2CY0		0E1 3330-73000-3AX0						
88-350 V DC	20 A	32. 3330 OMBOO 2C10	6EP1336-3BA10			6EP1336-1LB00				
600 V DC	20 A					11.1550 12500				6EP1536-3AA00
18							1) Conr	action to two phases 23	0_500 V AC _ sheet 24/25	5, SITOP PSU200M 1-/2-phase
							, COIII	icciion to two phases 23	0 300 V AC - SHEEL 24/23	, 51101 130200W 172-pHase

Special designs
6EP1331-1LD00
OLI 1331-1LDOO
6EP1332-1LD00
6EP1332-1LD10
6EP1333-1AL12
6EP1333-7CA00
6EP1333-1LD00
6EP1333-TLD00
6EP1334-1AL12
6EP3343-0SA00-0AY0
6EP1334-1LD00
6EP1433-0AA00
6ES7148-4PC00-0HA0
6EP3436-8UB00-0AY0
0EF3430-80B00-0AT0
6EP3437-8UB00-0AY0
6EP3437-8UB00-0AY0
6EP1732-0AA0 (as of 48 V DC)

Input voltage	Output current	Advanced po	ower supplies	Standard po	Standard power supplies		Basic power supplies		Special designs and applications
		SITOP PSU8600	SITOP PSU8200	SITOP PSU6200	SITOP smart	LOGO!Power	SITOP compact		
Output voltage 5, 12, 15, 48, etc	., V DC								
1-phase 120 V, 230 V AC		6EP3336-8SB00-2CY0							
	5 V/3 A					6EP3310-6SB00-0AY0			
	5 V/6.3 A					6EP3311-6SB00-0AY0			
	12 V/0.9 A					6EP3320-6SB00-0AY0			
	12 V/1.9 A			CER2224 7CR00 04V0		6EP3321-6SB00-0AY0	CED4224 ED400		
	12 V/2.0 A 12 V/3.0 A			6EP3321-7SB00-0AX0			6EP1321-5BA00		6EP1321-1LD00
	12 V/3.0 A 12 V/4.5 A					(FD2222 (CD00 04)/0			6EP1321-1LD00
	12 V/4.5 A 12 V/6.5 A					6EP3322-6SB00-0AY0	6EP1322-5BA10		
	12 V/6.5 A 12 V/7 A			6EP3323-7SB00-0AX0	6FD1222 2DA00		DEP1322-5BA10		
	12 V/7 A 12 V/8.3 A			0EP3323-73BUU-UAAU	DEP 1322-2BAUU				6EP1322-1LD00
	12 V/0.3 A 12 V/12 A			6EP3324-7SB00-3AX0					0EF1322-1LD00
	12 V/12 A			0EF3324-73B00-3AX0	6EP1323-2BA00				
	15 V/1.9 A				OLI 1323 2B/100	6EP3321-6SB10-0AY0			
	15 V/4 A					6EP3322-6SB10-0AY0			
	48 V/5 A			6EP3344-7SB00-3AX0		02.3322 033.0 0,0			6EP3344-0SB00-0AY0
	3-52 V/			02.331173300 37170					
	2-10 A								6EP3343-0SA00-0AY0
	2 x 15 V/								6555555 06466 05V6
	3.5 A								6EP3323-0SA00-0BY0
24 V DC	12 V/2.5 A							6EP1621-2BA00	
	12 V/8 A							6EP3123-0TA00-0AY0	
	12 V/15 A							6EP3124-0TA00-0AY0	
3-phase	4-28 V/20 A	6EP3436-8SB00-2CY0							
400-500 V AC	4–28 V/ 4 x 5 A	6EP3436-8MB00-2CY0							
	4-28 V/	6EP3437-8SB00-2CY0							
	40 A								
	4-28 V/ 4 x 10 A	6EP3437-8MB00-2CY0							
	12 V/20 A								6EP3424-8UB00-0AY0
	36 V/13 A		6EP3446-8SB10-0AY0						
	48 V/10 A		6EP3446-8SB00-0AY0						
	48 V/20 A		6EP3447-8SB00-0AY0						

SITOP PSU8600 advanced power supplies The power supply system for digitalization and industry 4.0

		COMMITSE ACLIS	The second secon	DOMPTISH HOLES	
Technical data	SITOP PSU8600 1- and 2-phase ¹⁾	SITOP PSU8600 3-		SITOP PSU8600 3-phase basic	SITOP PSU8600 3-phase basic
Output voltage/current, type	basic unit, 4 outputs 24 V/20 A/4x5 A, PSU8600	24 V/20 A, PSU8600	24 V/40 A, PSU8600	unit, 4 outputs 24 V/20 A/4x5 A, PSU8600	unit, 4 outputs 24 V/40 A/4x10 A, PSU8600
Article No.	6EP3336-8MB00-2CY0	6EP3436-8SB00-2AY0	6EP3437-8SB00-2AY0	6EP3436-8MB00-2CY0	6EP3437-8MB00-2CY0
Rated input voltage	100-240 V AC, 110-220 V DC	400–500 V 3 AC	400–500 V 3 AC	400–500 V 3 AC	400–500 V 3 AC
- Range	85275 V AC, 93275 V DC	320575 V 3 AC	320575 V 3 AC	320575 V 3 AC	320575 V 3 AC
Mains buffering	> 20 ms (at 100 V), extendable via buffer mod-				3203/3 V 3 AC
Mains buriefing	ule or UPS module	> 13 1115 (at 400 v), exteriuable	via buttet filodules alid OF3 filo	duie	
Rated line frequency	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz
Rated input current	5.4-2.4 A, 4.8-2.4 A	1.4-1.1 A	2.75-2.2 A	1.4–1.1 A	2.75-2.2 A
- Inrush current	< 15 A	< 14 A	< 14 A	< 14 A	< 14 A
 Recommended protection 	10–32 A character C or time-lag fuses	6–16 A charact. C 3-ph. coupled	l or 3RV2011-1DA10 (setting 3	A) or 3RV2711-1DD10	
Rated output voltage	24 V DC	24 V DC	24 V DC	24 V DC	24 V DC
- Tolerance	± 3%	± 3 %	± 3 %	± 3 %	± 3 %
 Setting range 	428 V DC	428 V DC	428 V DC	428 V DC	428 V DC
 Rated output current 	20 A, 4 outputs each with 5 A, number expandable via CNX modules	20 A, one output, number can be increased via CNX module	40 A, one output, number can be increased via CNX module	20 A, four outputs at 5 A each, number can be increased via CNX module	40 A, four outputs at 10 A each, number can be increased via CNX module
 Overload behavior (Extra Power) 	30 A for 5 s/min	30 A for 5 s/min	60 A for 5 s/min	30 A for 5 s/min	60 A for 5 s/min
- Derating	-	From +50 °C (2.5%/K); no derating to 480 W (40-A devices)	ng in connection with expansion	n module and total load of basic device	es' ouput up to 240 W (20-A devices) or
Switching threshold adjustment range	0.55 A	220 A	440 A	0.55 A	0.510 A
Shutdown behavior per output	Load current 101149 % of the setting: shutdow				
Efficiency at rated values, approx.	92%	93%	94%	93%	94%
Signaling contact "DC o. k."	Yes	Yes	Yes	Yes	Yes
Interface	Industrial Ethernet/PROFINET with two ports				
Parallel switching	Yes, output 1 with 2 or 3 with 4	Yes	Yes	Yes, output 1 with 2 or 3 with 4	Yes, output 1 with 2 or 3 with 4
Radio interference suppression (EN 55022)	Class B	Class B	Class B	Class B	Class B
Line harmonics limitation (EN 61000-3-2)	Yes	Yes	Yes	Yes	Yes
Degree of protection (EN 60529)	IP 20	IP20	IP20	IP20	IP20
Ambient temperature	−25+60 °C	−25+60 °C	−25+60 °C	−25+60 °C	−25+60 °C
Dimensions (W x H x D) in mm	125 x 125 x 150	80 x 125 x 150	125 x 125 x 150	100 x 125 x 150	125 x 125 x 150
Weight approx.	2.65 kg	1.8 kg	2.65 kg	2.0 kg	2.65 kg
Certification	CE, cULus, CB, cCSAus, IECEx, ATEX, CCC (further in preparation))	CE, cULus, CB, cCSAus, IECEx, AT	EX, CCC, cCSAus Class I Div 2, SI	EMI F47, DNV GL, ABS	
System expandability	Up to 4 expansion modules (CNX8600) and up to	2 buffer components (BUF8600,	UPS8600)		



^{1) 2-}phase connection to 240 V, e.g. in North America


Specifications at rated input voltage and ambient temperature at +25 °C (unless otherwise specified)

SITOP PSU8600 advanced power supplies The power supply system for digitalization and industry 4.0

Technical data Buffer time, type	100 ms/40 A, BUF8600	300 ms/40 A, BUF8600	r module 4 s/40 A, BUF8600	10 s/40 A, BUF8600	
Article No.	6EP4297-8HB00-0XY0	6EP4297-8HB10-0XY0	6EP4293-8HB00-0XY0	6EP4295-8HB00-0XY0	
Product/function					
description	can be used in a group of systems.	asic devices to extend buffering time during pow . Data and power are transmitted via the System	Clip Link connector.	nponents (801 0000, 01 30000)	
Internal energy storage	Electrolytic capacitors		Double-layer capacitors (Ultracap	os)	
Buffer time with 24 V DC and load current					
5 A	800 ms	2.4 s	40 s	80 s	
10 A	400 ms	1.2 s	20 s	40 s	
20 A	200 ms	600 ms	10 s	20 s	
40 A	100 ms	300 ms	4 s	10 s	
Typical charging time	19 s	54 s	5 min	10 min	
Max. power during buffer operation	60 A for 5 s/min	60 A for 5 s/min	40 A	60 A for 5 s/min	
Status messages via 3-color LED	Normal operation, state of charge,	, buffer operation, error	Normal operation, state of charge, buffer operation, error		
Status messages via signal contact	-		State of charge > x %, buffer oper	ation	
Status messages via PROFINET (basic unit)	Normal operation, state of charge,	, buffer operation, error	Normal operation, state of charge	e, buffer operation, error	
Additional functions	-		Remote on/off contact for deactive plant to prevent unnecessary disc	vating buffering, e.g., when shutting down the charge	
Degree of protection (EN 60529)	IP 20	IP 20	IP 20	IP 20	
Ambient temperature	−25+60 °C	−25+60 °C	−25+60 °C	−25+60 °C	
Dimensions (W x H x D) in mm	60 x 125 x 150	125 x 125 x 150	60 x 125 x 150	125 x 125 x 150	
Weight approx.	1.33 kg	2.26 kg	1.25 kg	1.95 kg	
Certification		CCC, cCSAus Class I Div 2, SEMI F47, DNV GL, ABS		K, CCC, cCSAus Class I Div 2, SEMI F47, DNV GL, ABs	
	11, color, co, comas, recen, men,		1_, 00 200, 00, 000, 100 A, 110 A, 110 A	,,,,,,,,,,,,	

Specifications at rated input voltage and ambient temperature at +25 °C (unless otherwise specified)









Technical data	Battery ı	module			
Туре	BAT8600 Pb	BAT8600 LiFePO4			
Article No.	6EP4145-8GB00-0XY0	6EP4143-8JB00-0XY0			
Product/function description	External energy storage device for UPS module UPS8600. Connection to the UPS module via plus and minus lines for power transmission as well as via the "Energy Storage Link" fo data transmission. The Energy Storage Link enables diagnosis and temperature-controlled charging for maximum battery service life. Up to five identical battery modules can be connected to one UPS module.				
Battery/storage technology	Lead (Pb)	Lithium iron phosphate (LiFePO4)			
Energy content	380 Wh	264 Wh			
Rated voltage	48 V DC	48 V DC			
Voltage range	42–58 V	42–58 V			
Status messages via 3-color LED	State of charge, battery test/ca replacement, overtemperature,				
Overload and short- circuit protection	Blade fuse 40 A/58 V	Blade fuse 40 A/58 V			
Parallel switching	yes, up to five (identical) units	yes, up to five (identical) units			
Degree of protection (EN 60529)	IP 20	IP 20			
Ambient temperature	−10+50 °C	−10+50 °C			
Installation	Wall mounting	Wall mounting			
Dimensions (W x H x D) in mm	322 x 187 x 110	322 x 187 x 110			
Weight approx.	13 kg	6.5 kg			
Certification	CE, UR, CB, cCSAus, IECEx, ATEX, CCC, cCSAus Class I Div 2, DNV GL, ABS	CE, CB, cCSAus, DNV GL, ABS			



	BAT8600 Pb	BAT8600 LiFePO4			
System output capacity	Buffer times¹)				
120 W	2 h 4 min	1 h 56 min			
240 W	57 min	60 min			
480 W	25 min	29 min			
720 W	19 min	22 min			
960 W	10 min	14 min			
Charging					

capacity	Chargh	ig tilles		
120 W/60 W (switchable)	2 h 45 min (120 W)	2 h 40 min (120 W)		
Ambient temperature	Service life ²⁾			
+ 20 °C	4 years	15 years		
+ 30 °C	2 years	10 years		
+ 40 °C	1 year	9 years		
+ 50 °C	0.5 years	2 years		

 $^{^{1)}}$ Typical buffer times for a new fully-charged battery module at 25° C

 $^{^{\}rm 2)}$ Typical end of service life according to EUROBAT: reduction to 80% of original capacity

Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

SITOP PSU8200 advanced power supplies Technology power supply for demanding applications

	OCENSA DO LA COMPANIA DE LA COMPANIA DEL COMPANIA DEL COMPANIA DE LA COMPANIA DE	oceanse double for the first the fir	STOR PRODUCTION	SITOP PRILIDAD	
Technical data		SITOP PSU	8200 1-phase		SITOP PSU200M 1-phase/2-phase ²⁾
Output voltage/current, type	24 V/5 A, PSU8200	24 V/10 A, PSU8200	24 V/20 A, PSU8200	24 V/40 A, PSU8200	24 V/5 A, PSU200M
Article No.	6EP3333-8SB00-0AY0	6EP3334-8SB00-0AY0	6EP1336-3BA10	6EP3337-8SB00-0AY0	6EP1333-3BA10
Rated input voltage – Range	120–230 V AC 85132/170264 V AC, automat	ic range switching	120–230 V AC 85275 V AC or 88350 V DC	120/230 V AC 85132/170264 V AC, automatic range switching	120–230/230–500 V AC 85264/176550 V AC
Mains buffering	> 35 ms (at 120/230 V)	> 35 ms (at 120/230 V)	> 20 ms (at 120/230 V)	> 25 ms (at 230 V)	> 25 ms (at 120/230 V)
Rated line frequency	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz
Rated input current – Inrush current ¹⁾ – Recommended miniature circuit breaker	2.1/1.2 A < 10 A 6 A charact. C or 3RV1021-1xA10	4.0/1.9 A < 10 A 10 A charact. C or 3RV1021-1xA10	4.6–2.5 A < 20 A 10 A charact. C or 3RV1021-1xA10	15.0/8.0 A < 50 A 20 A charact. C or 3RV2411-xxA10	2.2–1.2/1.2–0.61 A < 35 A 6 A charact. C or 3RV2011-1xA10
Rated output voltage – Tolerance – Setting range	24 V DC ± 3 % 2428.8 V DC	24 V DC ± 3 % 2428.8 V DC	24 V DC ± 3 % 2428.8 V DC	24 V DC ± 3 % 2428.8 V DC	24 V DC ± 3 % 2428.8 V DC
Rated output current	5 A	10 A	20 A	40 A	5 A
Overload behavior (power boost for 25 ms)Overload behavior	15 A 7.5 A	30 A 15 A	60 A 30 A	120 A 60 A	15 A No
(extra power for 5 s/min)	7.57.	1371	3071	30 A	
– Derating	-	from +60 °C (2 %/K)	from +60 °C (3 %/K)	from +60 °C (2.5 %/K)	from +60 °C (2 %/K)
Efficiency at rated values, approx.	93 %	94 %	93 %	92 %	88 %
Signaling contact "DC o. k."	Yes	Yes	Yes	Yes	Yes
Remote On/Off	Yes	Yes	No	No	No
Parallel switching	Yes, output characteristic can be s	witched to parallel operation			
Electronic short-circuit protection	Yes, constant current or latching s	shutdown selectable; constant curr	ent: approx. 1.15 x rated output curi	rent	
Radio interference suppression (EN 55022)	Class B	Class B	Class B	Class B	Class B
Supply harmonics limitation	yes (EN 61000-3-2)	yes (EN 61000-3-2)	yes (EN 61000-3-2)	yes (EN 61000-3-2)	yes (EN 61000-3-2)
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20	IP20
Ambient temperature	−25+70 °C	−25+70 °C	−25+70 °C	−25+70 °C	−25+70 °C
Dimensions (W x H x D) in mm	45 x 125 x 125	55 x 125 x 125	90 x 125 x 125	145 x 145 x 150	70 x 125 x 121
Weight approx.	0.8 kg	1 kg	1.5 kg	3.1 kg	0.6 kg
Certification	CE, cULus, CB, ATEX, IECEx, CCC, o DNV GL, ABS	CSAus Class I Div 2, SEMI F47 ³⁾ ,	CE, cULus, ATEX, IECEx, CCC, UL Class I Div 2, DNV GL, ABS	CE, cULus, CB, ATEX, IECEx, CCC, cCSAus Class I Div 2, SEMI F47 ⁴), DNV GL, ABS	CE, cULus, CB, ATEX, IECEx, CCC, UL Class I Div 2, SEMI F47 ³⁾ , DNV GL, ABS

¹⁾ Inrush current can be limited by using a SITOP inrush current limiter: 6EP4683-6LB00-0AY0 (max. 5 A, 100–240 V AC) or 6EP1967-2AA00 (max. 10 A, 100–480 V AC, 1 unit per phase required). 2) Connection to two phases of a three-phase supply network 3) At an input voltage of 208–230 V AC 4) In combination with two buffer modules. Technical data applies at rated input voltage and ambient temperature of +25°C (unless otherwise specified).













SITOP PSU200M 1-phase/2-phase ²⁾	SITOP P	5U8200 3-phase	SITOP PSU8200 3-phase, 36 V	SITOP PSU820	00 3-phase, 48 V
24 V/10 A, PSU200M	24 V/20 A, PSU8200	24 V/40 A, PSU8200	36 V/13 A, PSU8200	48 V/10 A, PSU8200	48 V/20 A, PSU8200
6EP1334-3BA10	6EP3436-8SB00-0AY0	6EP3437-8SB00-0AY0	6EP3446-8SB10-0AY0	6EP3446-8SB00-0AY0	6EP3447-8SB00-0AY0 ⁴⁾
120–230/230–500 V AC 85264/176550 V AC	400–500 V 3 AC 320575 V 3 AC	400–500 V 3 AC 320575 V 3 AC	400–500 V 3 AC 320575 V 3 AC	400–500 V 3 AC 320575 V 3 AC	400–500 V 3 AC 320575 V 3 AC
> 25 ms (at 120/230 V)	> 15 ms (at 400 V)	> 10 ms (at 400 V)	> 15 ms (at 400 V)	> 15 ms (at 400 V)	> 10 ms (at 400 V)
50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz
4.4–2.4/2.4–1.1 A < 35 A 6 A charact. C or 3RV2011-1xA10	1.2–1.0 A < 18 A 6–16 A charact. C 3-ph. coupled or 3RV2011-1DA10 or 3RV2711-1DD10	2.1–1.7 A < 13 A 10–16 A charact. C 3-ph. coupled or 3RV2011-1DA10 or 3RV2711-1DD10	1.2–1.0 A < 18 A 6–16 A charact. C 3-ph. coupled or 3RV2011-1DA10 or 3RV2711-1DD10	1.2–1.0 A < 18 A 6–16 A charact. C 3-ph. coupled or 3RV2011-1DA10 or 3RV2711-1DD10	2–1.7 A < 13 A 10–16 A charact. C 3-ph. coupled or 3RV2011-1DA10 or 3RV2711-1DD10
24 V DC ± 3 % 2428.8 V DC	24 V DC ± 3 % 2428.8 V DC	24 V DC ± 3 % 2428 V DC	36 V DC ± 3 % 3240 V DC	48 V DC ± 3 % 4256 V DC	48 V DC ± 3 % 4656 V DC
10 A	20 A	40 A	13 A	10 A	20 A
30 A	60 A	120 A	39 A	23 A	60 A
No	30 A	60 A	19.5 A	15 A	30 A
from +60 °C (2 %/K)	from +60 °C (3 %/K)	from +60 °C (4 %/K)	from +60 °C (3 %/K)	from +60 °C (3 %/K)	from +60 °C (4 %/K)
91 %	94%	94%	94%	93 %	94%
Yes	Yes	Yes	Yes	Yes	Yes
No	Yes	Yes	Yes	Yes	Yes
Yes, output characteristic can be sv	witched to parallel operation				
Yes, constant current or latching sh	nutdown selectable; constant current	: approx. 1.15 x rated output current			
Class B	Class B	Class B	Class B	Class B	Class B
yes (EN 61000-3-2)	yes (EN 61000-3-2)	yes (EN 61000-3-2)	yes (EN 61000-3-2)	yes (EN 61000-3-2)	yes (EN 61000-3-2)
IP20	IP20	IP20	IP20	IP20	IP20
−25+70 °C	−25+70 °C	−25+70 °C	−10+70 °C	−25+70 °C	−25+70 °C
70 x 125 x 121	70 x 125 x 125	135 x 145 x 150	70 x 125 x 125	70 x 125 x 125	135 x 145 x 150
1.4 kg	1.2 kg	3.3 kg	1.2 kg	1.2 kg	3.3 kg
CE, cULus, CB, ATEX, IECEx, CCC, UL Class I Div 2, SEMI F47 ³⁾ , DNV GL, ABS	CE, cULus, CB, ATEX, IECEx, CCC, UL Class I Div 2, SEMI F47, DNV GL, ABS	CE; cULus, CB, ATEX, IECEx, CCC, cCSAus Class I Div 2, SEMI F47, DNV GL, ABS	CE, cULus, CB, CCC, cCSAus Class I Div 2	CE, cULus, CB, ATEX, IECEx, CCC, cCSAus Class I Div 2, DNV GL, ABS	CE, cULus, CB, ATEX, IECEx, CCC, cCSAus Class I Div 2, SEMI F47

New: SITOP PSU6200 standard power supplies The all-around power supply for a wide range of applications

						New: Ex version
Technical data			SITOP PSU6200 1-phase			
Output voltage/current, type	12 V/2 A, PSU6200	24 V/1.3 A, PSU6200	24 V/2,5 A, PSU6200	12 V/7 A, PSU6200	24 V/3,7 A, PSU6200	24 V/5 A, PSU6200
Article No. Article No. Ex version	6EP3321-7SB00-0AX0	6EP3331-7SB00-0AX0	6EP3332-7SB00-0AX0	6EP3323-7SB00-0AX0	6EP3333-7LB00-0AX0	6EP3333-7SB00-0AX0 6EP3333-7SC00-0AX0
Rated input voltage	120-230 V AC/120-240 V D	С		120-230 V AC/120-240 V D	C	
– Range	85-264 V AC/110-275 V DC			85-264 V AC/99-275 V DC		
Mains buffering	150 ms at Uin = 230 V	150 ms at Uin = 230 V	150 ms at Uin = 230 V	90 ms at Uin = 230 V	90 ms at Uin = 230 V	80 ms at Uin = 230 V
Rated line frequency	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz
Rated input current	0.5/0.3 A	0.6/0.3 A	1.1/0.6 A	1.4/0.8 A	1.5/0.9 A	1.9/1.1 A
– Inrush current ¹⁾	< 32 A	< 32 A	< 32 A	< 29 A	< 29 A	< 29 A
– Recom. miniature circuit breaker	from 6 A characteristic C	from 6 A characteristic C	from 6 A characteristic			
Rated output voltage	12 V	24 V	24 V	12 V	24 V	24 V
– Tolerance	± 3%	± 3%	± 3%	± 3%	± 3%	± 3%
– Setting range	10.5–12.9 V	22.2–26.4 V	22.2-26.4 V	12-15.5 V	24-28 V	24-28 V
Rated output current	2 A	1.3 A	2.5 A	7 A	3.7 A	5 A
– Permanently up to +45 °C	2 A	1.3 A	2.5 A	8.4 A	3.7 A	6 A
 Overload behavior (extra power for 5 s/min) 	-	-	-	150%	-	150%
– Derating	_	from +60 °C (2.5%/K)	from +60 °C (1.5%/K)	from +60 °C (2%/K)	_	from +60 °C (2%/K)
Efficiency at rated values, approx.	83.3%	86.3%	89%	87.1%	89.3%	90.2%
Signaling contact	No	No	No	DC o.k.	DC o.k.	DC o.k.
Parallel switching	No	No	No	No	No	No
Electronic short-circuit protection	Yes, restart	Yes, restart	Yes, restart	Yes, constant current (< 9 V hiccup)	Yes, constant current (< 15 V hiccup)	Yes, constant current (< 15 V hiccup)
Radio interfer. suppression (EN 55022)	Class B	Class B	Class B	Class B	Class B	Class B
Supply harmonics limitation (EN 61000-3-2)	Not applicable	Not applicable	Not applicable	Yes	Yes	Yes
Degree of protection (EN 60529)	IP 20	IP 20	IP 20	IP 20	IP 20	IP 20
Ambient temperature	Operation –25+70 °C				Operation –30 +70 °C, st	artup starting from -40°C
Dimensions (W x H x D) in mm	25 x 100 x 88	25 x 100 x 88	40 x 100 x 88	35 x 135 x 125	35 x 135 x 125	35 x 135 x 125
Weight approx.	0.2 kg	0.2 kg	0.25 kg	0.7 kg	0.7 kg	0.7 kg
Certification	3	3	9	4 V/1.3 A; 2.5 A. NEC Class 2: 3	3	3

New: Ex version

	New: Ex version	- Marie	New: Ex version			
	SITOP PSU	6200 1-phase			SITOP PSU6200 3-phase	
12 V/12 A, PSU6200	24 V/10 A, PSU6200	48 V/5 A, PSU6200	24 V/20 A, PSU6200	24 V/5 A, PSU6200	24 V/10 A, PSU6200	24 V/20 A, PSU6200
6EP3324-7SB00-3AX0	6EP3334-7SB00-3AX0 6EP3334-7SC00-3AX0	6EP3344-7SB00-3AX0	6EP3336-7SB00-3AX0 6EP3336-7SC00-3AX0	6EP3433-7SB00-0AX0	6EP3434-7SB00-3AX0	6EP3436-7SB00-3AX0
120-230 V AC/110-240 V DC				400–500 V 3 AC		
85–264 V AC/85–275 V DC				323 576 V 3 AC/450600 V DC		
70 ms at Uin = 230 V	45 ms at Uin = 230 V	46 ms at Uin = 230 V	25 ms at Uin = 230 V	20 ms at Uin = 400 V	30 ms at Uin = 400 V	25 ms at Uin = 400 V
50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz
1.4/0.8 A	2.2/1.2 A	2.2/1.2 A	4.3/2.3 A	0.33/0.28 A	0.39/0.32 A	0.77/0.62 A
: 6 A	< 6 A	< 6 A	< 12 A	< 22 A	< 13 A	< 17 A
rom 6 A characteristic C	from 10 A characteristic C	from 10 A characteristic C	from 10 A characteristic C	410 A char. C 3-ph. coupled ²⁾	416 A characteristic C 3-p	•
12 V	24 V	48 V	24 V	24 V	24 V	24 V
± 3% 12–15.5 V	± 3% 24–28 V	± 3% 48–56 V	± 3% 24–28 V	± 3% 24–28 V	± 3% 24–28 V	± 3% 24–28 V
12 A	10 A	5 A	24-26 V 20 A	5 A	10 A	24-28 V 20 A
14.4 A	12 A	6 A	24 A	6 A	12 A	24 A
150%	150%	150%	150%	150%	150%	150%
150%	150%	150%	150%	150%	150%	150%
rom +60 °C (2%/K)	from +60 °C (2%/K)	from +60 °C (3%/K)	from +60 °C (1%/K)	from +60 °C (3%/K)	from +60 °C (3%/K)	from +60 °C (3%/K)
39.3%	92.8%	93.9%	95.5%	91.2%	95.4%	95.9%
OC o.k./Diagnose	DC o.k./Diagnose	DC o.k./Diagnose	DC o.k./Diagnose	DC o.k.	DC o.k./Diagnose	DC o.k./Diagnose
es, 2 units	Yes, 2 units	Yes, 2 units	Yes, 2 units	No	Yes, 2 units	Yes, 2 units
/es, constant current < 9 V hiccup)	Yes, constant current (< 15 V hiccup)	Yes, constant current (< 30 V hiccup)	Yes, constant current (< 15 V hiccup)	Yes, constant current (< 15 V hiccup)	Yes, constant current (< 15 V hiccup)	Yes, constant current (< 15 V hiccup)
Class B	Class B	Class B	Class B	Class B	Class B	Class B
⁄es	Yes	yes	Yes	Yes	Yes	Yes
P 20	IP 20	IP 20	IP 20	IP 20	IP 20	IP 20
-25+70 °C, startup starting from –40 °C	Operation –30 +70 °C, star	tup starting from –40°C				
15 x 135 x 125	45 x 135 x 125	45 x 135 x 125	70 x 135 x 155	35 x 135 x 125	45 x 135 x 155	70 x 135 x 155
).9 kg	0.9 kg	0.9 kg	1.5 kg	0.7 kg	0.9 kg	1.5 kg
CE, cULus, cCSAus, CB, SEMI F SEP3336-7SC00-3AX0	47, in preparation: DNV GL, AB	S. ATEX, IECEx, CCC: 6EP3334-7	7SC00-3AX0,	CE, cULus, SEMI F47, in preparation:		, and the second

SITOP smart standard power supplies The high-performance standard power supply

	State of the last	The second secon								
Technical data		SITOP smart 1-phase								
Output voltage/current, type	24 V/2.5 A, PSU100S	24 V/5 A, PSU100S	12 V/7 A, PSU100S	24 V/10 A, PSU100S	12 V/14 A, PSU100S	24 V/20 A, PSU100S				
Article No.	6EP1332-2BA20	6EP1333-2BA20	6EP1322-2BA00	6EP1334-2BA20	6EP1323-2BA00	6EP1336-2BA10				
Rated input voltage	120/230 V AC	120/230 V AC	120/230 V AC	120/230 V AC	120/230 V AC	120/230 V AC				
– Range	85132/170264 V AC, au	tomatic range switching								
Mains buffering	> 20 ms (at 93/187 V)	> 20 ms (at 93/187 V)	> 20 ms (at 93/187 V)	> 20 ms (at 93/187 V)	> 20 ms (at 93/187 V)	> 20 ms (at 120/230 V)				
Rated line frequency	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz				
Rated input current – Inrush current ¹⁾ – Recommended miniature circuit breaker	1.25 A/0.74 A < 33 A from 3 A characteristic C	2.34 A/1.36 A < 40 A from 6 A characteristic C	1.73 A/0.99 A < 45 A from 6 A characteristic C	4.49 A/1.91 A < 60 A from 10 A characteristic C	3.24 A/1.41 A < 60 A from 10 A characteristic C	7.5/3.5 A < 11 A from 10 A characteristic C				
Rated output current - Tolerance - Setting range	24 V DC ± 3 % 22.828 V DC	24 V DC ± 3 % 22.828 V DC	12 V DC ± 3 % 11.515.5 V DC	24 V DC ± 3 % 22.828 V DC	12 V DC ± 3 % 11.515.5 V DC	24 V DC ± 3 % 2428 V DC				
Rated output current - Permanently up to +45 °C - Overload behavior (extra power for 5 s/min) - Derating	2.5 A 3 A 3.75 A from +60 °C (3 %/K)	5 A 6 A 7.5 A from +60 °C (3 %/K)	7 A 7 A 10.5 A from +55 °C (5 %/K)	10 A 12 A 15 A from +60 °C (3 %/K)	14 A 14 A 21 A from +55 °C (5 %/K)	20 A 24 A 30 A from + 60 °C (5 %/K)				
Efficiency at rated values, approx.	85%	88 %	84 %	90%	87%	90%				
Signaling contact "DC o. k."	Yes	Yes	Yes	Yes	Yes	Yes				
Parallel switching	Yes	Yes	Yes	Yes	Yes	Yes				
Elec. short-circuit protection	Yes, constant current	Yes, constant current	Yes, constant current	Yes, constant current	Yes, constant current	Yes, restart				
Radio int. sup. (EN 55022)	Class B	Class B	Class B	Class B	Class B	Class B				
Supply harmonics limitation (EN 61000-3-2)	Not applicable	Yes	Yes	Yes	Yes	Yes				
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20	IP20	IP20				
Ambient temperature	−25+70 °C	−25+70 °C	−25+70 °C	−25+70 °C	−25+70 °C	−25+70 °C				
Dimensions (W x H x D) in mm	32.5 x 125 x 120	50 x 125 x 120	50 x 125 x 120	70 x 125 x 120	70 x 125 x 120	115 x 145 x 150				
Weight approx.	0.32 kg	0.5 kg	0.5 kg	0.8 kg	0.8 kg	2.4 kg				
Certification	CE, cULus, CB, ATEX, IECEx, CCC, cCSAus Class I Div 2, DNV GL, BV	CE, cULus, CB, ATEX, IECEx, CCC, cCSAus Class I Div 2, DNV GL, BV	CE, cULus, CB, ATEX, IECEx, CCC, cCSAus Class I Div 2, DNV GL	CE, cULus, CB, ATEX, IECEx, CCC, cCSAus Class I Div 2, DNV GL, BV	CE, cULus, CB, ATEX, IECEx, CCC, cCSAus Class I Div 2, DNV GL	CE, cULus, CB, ATEX, IECEX, CCC, cCSAus Class I Div 2, DNV GL				

¹⁾ Inrush current can be limited by a SITOP inrush current limiter: 6EP4683-6LB00-0AY0 (max. 5 A, 100–240 V AC) or 6EP1967-2AA00 (max. 10 A, 100–480 V AC, 3 units required for 3 phases)

Technical data applies at rated input voltage and ambient temperature of +25°C (unless otherwise specified).









	SITO	P smart 3-phase	
24 V/5 A, PSU300S	24 V/10 A, PSU300S	24 V/20 A, PSU300S	24 V/40 A, PSU300S
6EP1433-2BA20	6EP1434-2BA20	6EP1436-2BA10	6EP1437-2BA20
400-500 V 3 AC	400-500 V 3 AC	400–500 V 3 AC	400–500 V 3 AC
340550 V 3 AC	340550 V 3 AC	340550 V 3 AC	340550 V 3 AC
> 6 ms (at 400 V)	> 6 ms (at 400 V)	> 6 ms (at 400 V)	> 6 ms (at 400 V)
50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz
0.45–0.4 A < 40 A 6–16 A charact. C 3-ph. coupled or 3RV2011-1DA10 or 3RV2711-1DD10	0.7–0.6 A < 50 A 6–16 A charact. C 3-ph. coupled or 3 RV2011-1DA10 or 3 RV2711-1DD10	1.2–1.0 A < 36 A 6–16 A charact. C 3-ph. coupled or 3 RV2011-1DA10 or 3 RV2711-1DD10	2.0–1.5 A < 60 A 10–16 A charact. C 3-ph. coupled or 3 RV2011-1DA10 or 3 RV2711-1DD10
24 V DC ± 3 % 2428 V DC	24 V DC ± 3 % 2428 V DC	24 V DC ± 3 % 2428 V DC	24 V DC ± 3 % 2428 V DC
5 A 6 A 7.5 A	10 A 12 A 15 A	20 A 24 A 30 A	40 A 48 A 60 A
from +60 °C (3 %/K)	from +60 °C (3 %/K)	from +60 °C (5 %/K)	from +60 °C (2.5 %/K)
89 %	91 %	91 %	91.5 %
Yes	Yes	Yes	Yes
Yes	Yes	Yes	Yes
Yes, constant current	Yes, constant current	Yes, restart	Yes, restart
Class B	Class B	Class B	Class B
Yes	Yes	Yes	Yes
IP20	IP20	IP20	IP20
−25+70 °C	−25+70 °C	0+70 °C	0+70 °C
50 x 125 x 120	70 x 125 x 120	90 x 145 x 150	150 x 145 x 150
0.43 kg	0.67 kg	1.6 kg	3.7 kg
CE, cULus, CB, ATEX, UL Class I Div 2, IECEx, CCC, DNV GL, ABS	CE, cULus, CB, ATEX, UL Class I Div 2, IECEx, CCC, DNV GL, ABS	CE, cULus, CB, ATEX, UL Class I Div 2, IECEx, CCC, DNV GL, ABS	CE, cULus, CB, ATEX, cCSAus Class I Div 2, IECEx, CCC, DNV GL, ABS

LOGO!Power basic power supplies Flat power supply for distribution boards

Technical data	18-mm	n design			36-mm design	
Output voltage/current	12 V/0.9 A	24 V/0.6 A	5 V/3 A	12 V/1.9 A	15 V/1.9 A	24 V/1.3 A
NEC Class 2	Yes	Yes	Yes	Yes	Yes	Yes
Article No.	6EP3320-6SB00-0AY0	6EP3330-6SB00-0AY0	6EP3310-6SB00-0AY0	6EP3321-6SB00-0AY0	6EP3321-6SB10-0AY0	6EP3331-6SB00-0AY0
Rated input voltage – Range	100–240 V AC 85264 V AC/110300 V DC		100–240 V AC 85264 V AC/110300	0 V DC		
Mains buffering	> 40 ms (at 187 V)	> 40 ms (at 187 V)	> 40 ms (at 187 V)			
Rated line frequency	50/60 Hz	50/60 Hz	50/60 Hz			
Rated input current - Inrush current ¹⁾	0.3-0.2 A < 20 A	0.3-0.2 A < 20 A	0.36-0.22 A < 26 A	0.53-0.30 A < 25 A	0.63-0.33 A < 25 A	0.70-0.35 A < 25 A
 Recommended miniature circuit breaker 	from 6 A characteristic B or from	om 2 A characteristic C	from 6 A characteristic	B or from 2 A characteris	tic C	
Rated output voltage - Tolerance - Setting range	12 V DC ± 3 % None	24 V DC	5 V DC ± 3 % 4.65.4 V DC	12 V DC 10.516.1 V DC	15 V DC 10.516.1 V DC	24 V DC 22.226.4 V DC
Rated output current - Overload behavior on startup - Derating	0.9 A 1.35 A (for 200 ms)	0.6 A 0.9 A (for 200 ms)	3.0 A 4.5 A (for 200 ms) from +55 °C (2 %/K)	1.9 A 2.85 A (for 200 ms) from +55 °C (2 %/K)	1.9 A 2.85 A (for 200 ms) from +55 °C (2 %/K)	1.3 A 1.95 A (for 200 ms) from +55 °C (2 %/K)
Efficiency at rated values, approx.	78%	81 %	76%	81%	83 %	86%
Signaling contact "DC o. k."	No		No	No	No	No
Parallel switching	No	No	Yes	Yes	Yes	Yes
No-load loss	< 0.3 W		< 0.3 W			
Electronic short-circuit protection	Yes, constant current		Yes, constant current			
Radio interference suppression (EN 55022)	Class B		Class B			
Supply harmonics limitation (EN 61000-3-2)	Not applicable		Not applicable			
Degree of protection (EN 60529)	IP20		IP20			
Ambient temperature	−25 +70 °C		−25 +70 °C			
Dimensions (W x H x D) in mm	18 x 90 x 53		36 x 90 x 53			
Weight approx.	0.07 kg	0.07 kg	0.12 kg			
Certification	CE, CB Scheme, cULus, cURus, Class 1 Div 2, FM, SEMI F47, D		CC, CE, CB Scheme, cULus, cURus, NEC Class 2, ATEX, IECEx, CCC, Class 1 Div 2, FM, SEMI F47, DNV GL, ABS, EAC CE, CB Scheme, cULus, cURus, NEC Class 2, ATEX, IECEx, CCC, Class 2, ATEX, IECEx, CCC, Class 1 Div 2, FM, SEMI F47, DNV GL, ABS, EAC CE, CB Scheme, cULus, cURus, NEC Class 2, ATEX, IECEx, CCC, Class 1 Div 2, FM, SEMI F47, DNV GL, ABS, EAC BV, LRS, EAC			





Technical data			72-mm design		
Output voltage/current	5 V/6.3 A	12 V/4.5 A	15 V/4 A	24 V/2.5 A	24 V/4 A
NEC Class 2	no	no	yes	yes	no
Article No.	6EP3311-6SB00-0AY0	6EP3322-6SB00-0AY0	6EP3322-6SB10-0AY0	6EP3332-6SB00-0AY0	6EP3333-6SB00-0AY0
Rated input voltage – Range	100–240 V AC 85264 V AC/110300 V DC				100–240 V AC 85264 V AC/110300 V DC
Mains buffering	> 40 ms (at 187 V)				> 40 ms (at 187 V)
Rated line frequency	50/60 Hz				50/60 Hz
Rated input current — Inrush current 1)	0.71–0.37 A < 50 A	1.13–0.61 A < 50 A	1.24–0.68 A < 55 A	1.22–0.66 A < 52 A	1.95–0.97 A < 31 A
 Recommended miniature circuit breaker 	from 10 A characteristic B or fro	m 6 A characteristic C			from 10 A characteristic B or from 6 A characteristic C
Rated output voltage – Tolerance – Setting range	5 V DC ± 3 % 4.65.4 V DC	12 V DC 10.516.1 V DC	15 V DC 10.516.1 V DC	24 V DC 22.226.4 V DC	24 V DC ± 3 % 22.226.4 V DC
Rated output current - Overload behavior on startup - Derating	6.3 A 9.45 A (for 200 ms) from +55 °C (2 %/K)	4.5 A 6.75 A (for 200 ms) from +55 °C (2%/K)	4.0 A 6.0 A (for 200 ms) from +55 °C (2%/K)	2.5 A 3.75 A (for 200 ms) from +55 °C (2 %/K)	4.0 A 6.0 A (for 200 ms) from +55 °C (2%/K)
Efficiency at rated values, approx.	80 %	87%	88%	90%	89 %
Signaling contact "DC o. k."	No	No	No	No	No
Parallel switching	Yes	Yes	Yes	Yes	Yes
No-load loss	< 0.3 W				< 0.3 W
Electronic short-circuit protection	Yes, constant current				Yes, constant current
Radio interference suppression (EN 55022)	Class B				Class B
Supply harmonics limitation (EN 61000-3-2)	Not applicable				Yes
Degree of protection (EN 60529)	IP20				IP20
Ambient temperature	−25 +70 °C				−25 +70 °C
Dimensions (W x H x D) in mm	54 x 90 x 53				72 x 90 x 53
Weight approx.	0.2 kg				0.29 kg
Certification	CE, CB Scheme, cULus, cURus, ATEX, IECEx, CCC, Class 1 Div 2, FM, SEMI F47, DNV GL, ABS, EAC	NEC Class 2, ATEX, IECEx, CCC,	CE, CB Scheme, cULus, cURus, NEC Class 2, ATEX, IECEx, CCC, Class 1 Div 2, FM, SEMI F47, DNV GL, ABS, EAC		CE, CB Scheme, cULus, cURus, ATEX, IECEx, CCC, Class 1 Div 2, FM, SEMI F47, DNV GL, ABS, SEMI F47, BV, LRS, EAC

SITOP lite basic power supplies The cost-effective basic power supply

		TOUTING BOXES	TOOLINSA HOLLS	
Technical data			SITOP lite	
Output voltage / current, type	24 V/2.5 A, PSU100L	24 V/5 A, PSU100L	24 V/10 A, PSU100L	24 V/20 A, PSU100L
Article No.	6EP1332-1LB00	6EP1333-1LB00	6EP1334-1LB00	6EP1336-1LB00
Rated input voltage – Range	120/230 V AC 93132/187264 V AC	120/230 V AC 93132/187264 V AC	120/230 V AC 93132/187264 V AC	100–240 V AC 85264 V AC/88370 V DC
Mains buffering	> 20 ms (at 93/187 V)			
Rated line frequency	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz
Rated input current – Inrush current ¹⁾	1.0/0.65 A < 27 A	2.1/1.15 A < 32 A	4.3/2.0 A < 65 A	5.55/2.35 A < 45 A
 Recommended miniature circuit breaker 	3 A characteristic C	6 A characteristic C	10 A characteristic C	10 A characteristic C
Rated output voltage – Tolerance – Setting range	24 V DC ± 3 % 22.826.4 V DC	24 V DC ± 3 % 22.826.4 V DC	24 V DC ± 3 % 22.826.4 V DC	24 V DC ± 3 % 22.828 V DC
Rated output current – Derating	2.5 A from +45 °C (1.5 %/K)	5 A from +45 °C (1.5 %/K)	10 A from +45 °C (2 %/K)	20 A from +45 °C (2.5 %/K)
Efficiency at rated values, approx.	85%	86%	89 %	92%
Signaling contact "DC o. k."	No	No	No	No
Parallel switching	Yes	Yes	Yes	Yes
Electronic short-circuit protection	Yes, constant current	Yes, constant current	Yes, constant current	Yes, constant current
Radio int. sup. (EN 55022)	Class A	Class A	Class A	Class B
Supply harmonics limitation (EN 61000-3-2)	Not applicable	No	No	Yes
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20
Ambient temperature	0 +60 °C	0 +60 °C	0 +60 °C	−25 +70 °C
Dimensions (W x H x D) in mm	32.5 x 125 x 120	50 x 125 x 120	70 x 125 x 120	110 x 125 x 125
Weight approx.	0.4 kg	0.5 kg	0.75 kg	1.8 kg
Certification	CE, cULus, CB-Scheme	CE, cULus, CB-Scheme	CE, cULus, CB-Scheme	CE, cULus, CB-Scheme

¹⁾ Inrush current can be limited by a SITOP inrush current limiter: 6EP4683-6LB00-0AY0 (max. 5 A, 100–240 V AC) or 6EP1967-2AA00 (max. 10 A, 100–480 V AC)

Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

SITOP in SIMATIC design

								9333	
Technical data	SIMATIC S7-1200 design		SIMATIC S7-300 design	ı	SIMATIC S7-	1500 design	SIMATIC E	T 200SP PS	SIMATIC ET 200pro design
Output voltage/current, type		24 V/2 A, PS307	24 V/5 A, PS307	24 V/10 A, PS307	24 V/3 A, PM1507	24 V/8 A, PM1507	24 V/5 A, PS	24 V/10 A, PS	24 V/8 A, ET 200pro PS
Article No.	6EP1332-1SH71	6ES7307-1BA01-0AA0	6ES7307-1EA01-0AA0	6ES7307-1KA02-0AA0	6EP1332-4BA00	6EP1333-4BA00	•		6ES7148-4PC00-0HA0
Rated input voltage	120/230 V AC, automati	c range selection							380-480 V 3 AC
- Range	85132/176264 V AC	85132/170264 V AC			85132/176264 V AC		85132/17026	4 V AC	340550 V 3 AC
Mains buffering	> 20 ms (at 93/187 V)								3 ms (at 400 V)
Rated line frequency	50/60 Hz								
Rated input current	1.2/0.67 A	0.9/0.5 A	2.3/1.2 A	4.2/1.9 A	1.4 A/0.8 A	3.7 A/1.7 A	2.3/ 1.4 A	4.5/1.9 A	1 A
- Inrush current ¹⁾	< 13 A	< 22 A	< 20 A	< 55 A	< 23 A	< 67 A	< 40 A	< 60 A	< 40 A
 Recommended miniature circuit breaker 	16 A charact. B, 10 A charact. C	3 A charact. C	6 A charact. C	10 A charact. C	from 6 A charact. C, from 10 A charact. B	from 10 A charact. C, from 16 A charact. B	6 A charact. C	10 A charact. C	3RV2021-4NA10
Rated output voltage	24 V DC	24 V DC	24 V DC	24 V DC	24 V DC	24 V DC	24 V DC	24 V DC	24 V DC
- Tolerance	± 3%	± 3%	± 3 %	± 3 %	± 3%	± 3%	± 3%	± 3%	- 5 %/+3 %
- Setting range	-	-	_	-	-	_	22.828 V DC	22.828 V DC	_
- On/off switch	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes	No
Rated output current	2.5 A	2 A	5 A	10 A	3 A	8 A	5 A	10 A	8 A
- Overload behavior (Extra Power for 5 s/min)	-	-	_	-	4.5 A	12 A	7.5 A	15 A	_
Efficiency at rated values, approx.	83 %	84%	87%	90 %	87 %	90%	88%	90%	88%
Signaling contact "DC o. k."	No	No	No	No	No	No	Yes	Yes	Yes, and for overtemperature
Parallel switching	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	No
Electronic short-circuit protection	Yes, constant current characteristic	Yes, restart	Yes, restart	Yes, restart	Yes, restart	Yes, restart	Yes, constant curi	ent characteristic	Yes, restart
Radio interference suppression (EN 55022)	Class B	Class B	Class B	Class B	Class B	Class B	Class B	Class B	EN 61000-6-4 (Class A)
Supply harmonics limitation (EN 61000-3-2)	Not applicable	Not applicable	Yes	Yes	Not applicable	Yes	Yes	Yes	No
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20	IP20	IP20	IP20	IP20	IP67, UL: encl. type 5 indoor
Ambient temperature	0+60 °C	0+60 °C	0+60 °C	0+60 °C	0+60 °C	0+60 °C	−30+70 °C	−30+70 °C	−25+55 °C
Installation	DIN rail or wall mounting	Can be mounted on S7 r 6EP1971-1BA00	ail; mounting adapter for	DIN rail 35 x15 mm:	on S7-1500 system carrier	on S7-1500 system carrier	DIN rail		Screw mounting, e.g., on ET 200pro system rail
Dimensions (W xH x D) in mm	70 x 100 x 75	40 x 125 x 120	60 x 125 x 120	80 x 125 x 120	50 x 147 x 135	75 x 147 x 135	160 x 117 x 75		310×135.5 ×90
Weight approx.	0.3 kg	0.4 kg	0.6 kg	0.8 kg	0.45 kg	0.74 kg	0.5 kg	0.8 kg	2.8 kg
Certification	J	J	JLus Class I Div 2, DNV GL	J	CE, cULus, CB, ATEX, IEC Div 2, FM, DNV GL, ABS,	Ex, CCC, cULus Class I	CE, cULus, CSA/UI GL, FM		CE, cULus508
					,				

¹⁾Inrush current can be limited by a SITOP inrush current limiter: 6EP4683-6LB00-0AY0 (max. 5 A, 100–240 V AC) or 6EP1967-2AA00 (max. 10 A, 100–480 V AC, 1 unit per phase required). Technical data applies at rated input voltage and ambient temperature of +25°C (unless otherwise specified

DC/DC converter

	Areas of a	pplication for DC/DC converters	
Typical voltage	12 – 60 V DC	110 – 220 V DC	600 – 900 V DC
Applications	Battery power, DC refreshing, galvanic isolation	Supply voltage	DC link converter
Industries, areas of application	Automated guided vehicles, ships	Power plants	Machine tools, wind energy plants
Suiting product line SITOP:	PSU3400	PSU3600 PSU6200 PSU8600 LOGO!Power PSU8200 Lite	PSU400M

	Summary table of SITOP DC/DC converters and power supply units with DC input											
SITOP	PSU3400			PSU3600		PSU6200		PSU8600	LOGO!Power	PSU8200	Lite	PSU400M
DC input voltage range	918 V	1432 V	2860 V	88250 V	85275 V	99275 V	110275 V	93275 V	110300 V	88350 V	88370 V	300900 V
Rated output voltage/current												
5 V									3 A, 6.3 A			
12 V		8 A, 15 A			12 A	7 A	2 A		0.9 A, 1.9 A, 4.5 A			
15 V				dual 3.5 A					1.9 A, 4 A			
24 V	4 A	5 A, 10 A	3.5 A, 5 A, 10 A	(2x1228 V)	10 A, 20 A	3.7 A, 5 A	1.3 A, 2,5 A		0.6 A, 1.3 A, 2.5 A, 4 A	20 A	20 A	20 A
428 V								4 x 5 A				
48 V					5 A							
052 V				flexi 10 A								

DC/DC converter











				The state of		400			
Technical data					DC/D0	Converter			
Output voltage / current, type	24 V/4 A, PSU3400	12 V/8 A, PSU3400	24 V/5 A, PSU3400	12 V/15 A, PSU3400	24 V/10 A, PSU3400	24 V/3,5 A NEC Class 2, PSU3400	24 V/5 A, PSU3400	24 V/10 A, PSU3400	24 V/20 A, PSU400M
Article No.	6EP3133-0TA10- 0AY0	6EP3123-0TA00- 0AY0	6EP3133-0TA00- 0AY0	6EP3124-0TA00- 0AY0	6EP3134-0TA00- 0AY0	6EP3233-0TA10-0AY0	6EP3233-0TA00- 0AY0	6EP3234-0TA00-0AY0	6EP1536-3AA00
Rated input voltage	12 V DC	24 V DC	24 V DC	24 V DC	24 V DC	48 V DC	48 V DC	48 V DC	600 V DC ¹⁾
– Range	918 V DC	1832 V DC, 1418 with derating possible	·	14 32 V DC, deratin	ng for 1418 V DC	28 60 V DC, startup fro	om 36 V, derating for 2	8–36 V	300900 V DC, startup from approx. 340 V
Mains buffering	> 2 ms	> 5 ms	> 5 ms	> 5 ms	> 5 ms	> 5 ms	> 5 ms	> 5 ms	-
Rated input current	9.0 A	4.5 A	5.5 A	8.4 A	10.8 A	1.9 A	2.7 A	5.4 A	0.85 A
– Inrush current	<15 A	<15 A	<15 A	< 15 A	< 15 A	<15 A	<15 A	< 15 A	< 8 A
 Recommended miniature circuit breaker (not necessary in case of feed-in by SITOP) 	16 A characteristic B or C	10 A characteristic B	or C	16 A characteristic B	or C	10 A characteristic B or 0	3	16 A characteristic B or C	-
Rated output voltage	24 V DC	12 V DC	24 V DC	12 V DC	24 V DC	24 V DC	24 V DC	24 V DC	24 V DC
- Tolerance	± 3%	± 3%	± 3%	± 2%	± 1%	± 3%	± 3%	± 1%	± 3 %
– Setting range	2428 V DC	1215.5 V DC	2428 V DC	1215.5 V DC	2428 V DC	2428 V DC	2428 V DC	2428 V DC	2428.8 V DC
Rated output current	4 A	8 A	5 A	15 A	10 A	3.5 A	5 A	10 A	20 A
- Overload behavior	_	_	6 A up to 40 °C	_	12 A up to 40 °C	-	6 A up to 40 °C	12 A up to 40 °C	30 A
– Derating	from +60 °C (2%/K)	from +60 °C (2%/K)	from +60 °C (2%/K)	from +60 °C (2%/K)	from +60 °C (2%/K)	-	from +60 °C (2%/K)	from +60 °C (2%/K)	from +60 °C (5.5 %/K), 300400 V DC, 824900 V DC
Efficiency at rated values, approx.	89%	89.4%	92.5%	91%	93%	90.4%	91.6%	93.5%	95 %
Signaling contact "DC o. k."	No	No	No	Yes	Yes	No	No	Yes	Yes
Parallel switching	Yes, 2 units	Yes, 2 units	Yes, 2 units	Yes, 2 units	Yes, 2 units	-	Yes, 2 units	Yes, 2 units	Yes, output line switchable
Electronic short-circuit protection	Yes, restart								Yes, constant current or latching shutdown selectable
Radio suppression level (EN 55022)	Class B	Class B	Class B	Class B	Class B	Class B	Class B	Class B	Class A (emission)
Line harmonics limitation (EN 61000-3-2)	Not applicable	Not applicable	Not applicable	Not applicable	Not applicable	Not applicable	Not applicable	Not applicable	No
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20	IP20	IP20	IP20	IP20	IP20
Ambient temperature	−25+70 °C	−25+70 °C	−25+70 °C	−25+70 °C	−25+70 °C	−25+70 °C	−25+70 °C	−25+70 °C	−25+70 °C
Installation	DIN rail								
Dimensions (W x H x D) in mm	32 x 100 x 100	32 x 100 x 100	32 x 100 x 100	42 x 125 x 120	42 x 125 x 120	32 x 100 x 100	32 x 100 x 100	42 x 125 x 120	90 x 125 x 125
Weight approx.	0.4kg	0.4kg	0.4kg	0.6 kg	0.6 kg	0.4kg	0.4kg	0.6kg	1.2 kg
Certification		<u> </u>	EP3233-0TA10-0AY0: N			3			CE, cULus, CB, DNV GL
	12, 00200, 1.00, III pr								, 10200, 00, 0 02


¹⁾ The SITOP PSU400M power supply is designed for connection to a DC link power system, which means that the input voltage rises and falls successively while charging the DC link. Hot plug-in and hot plug-out of the input voltage above 450 V is not allowed. The 6EP1566-3AA00 ballast device for limiting the voltage rise must be used for this purpose. Technical data applies at rated input voltage and ambient temperature of +25°C (unless otherwise specified).

SITOP in special designs and applications

Technical data Output voltage/current, type Article No. 6EP1321-1LD00 Rated input voltage 100–240 V AC - Range 85264 V AC Mains buffering > 15 ms (at 115/230 V) Rated line frequency 50/60 Hz Rated input current 0.75–0.5 A - Inrush current¹¹ < 60 A - Recommended miniature circuit breaker Rated output voltage 12 V DC - Tolerance ± 2% - Setting range 1114 V DC Rated output current 3 A - Derating from +50 °C (2.5 %/K) Efficiency at rated values, approx. Signaling contact "DC o. k." No Remote On/Off No Parallel switching Yes Electronic short-circuit protection Yes, restart Radio interference suppression (EN 55022) Supply harmonics limitation (EN 61000-3-2) Degree of protection IP20 (EN 60529) Ambient temperature -10+70 °C	24 V/2,1 A, PSU100D 6EP1331-1LD00 100-240 V AC 85264 V AC > 15 ms (at 115/230 V) 50/60 Hz 1.1-0.7 A	24 V/3,1 A, PSU100D 6EP1332-1LD00 100-240 V AC 85264 V AC > 15 ms (at 115/230 V)	Wall mounting 24 V/4,1 A, PSU100D 6EP1332-1LD10 100–240 V AC 85264 V AC	12 V/8,3 A, PSU100D 6EP1322-1LD00	24 V/6,2 A, PSU100D	
Article No. 6EP1321-1LD00 Rated input voltage 100–240 V AC Range 85264 V AC Mains buffering > 15 ms	6EP1331-1LD00 100-240 V AC 85264 V AC > 15 ms (at 115/230 V) 50/60 Hz	6EP1332-1LD00 100-240 V AC 85264 V AC > 15 ms	6EP1332-1LD10 100–240 V AC	6EP1322-1LD00	24 V/6,2 A, PSU100D	
Rated input voltage	100-240 V AC 85264 V AC > 15 ms (at 115/230 V) 50/60 Hz	100–240 V AC 85264 V AC > 15 ms	100-240 V AC			24 V/12,5 A, PSU100D
- Range 85264 V AC Mains buffering > 15 ms	85264 V AC > 15 ms (at 115/230 V) 50/60 Hz	85264 V AC > 15 ms			6EP1333-1LD00	6EP1334-1LD00
Mains buffering > 15 ms (at 115/230 V) Rated line frequency 50/60 Hz Rated input current 0.75–0.5 A - Inrush current') < 60 A - Recommended miniature circuit breaker Rated output voltage 12 V DC - Tolerance ± 2% - Setting range 1114 V DC Rated output current 3 A - Derating from +50 °C (2.5 %/K) Efficiency at rated values, approx. Signaling contact "DC o. k." No Remote On/Off No Parallel switching Yes Electronic short-circuit protection Yes, restart Radio interference suppression (EN 55022) Supply harmonics limitation (EN 61000-3-2) Degree of protection IP20 (EN 60529) Ambient temperature -10+70 °C	> 15 ms (at 115/230 V) 50/60 Hz	> 15 ms	85264 V AC	100-240 V AC	100-240 V AC	100-240 V AC
(at 115/230 V) Rated line frequency Rated input current - Inrush current - Recommended miniature circuit breaker Rated output voltage - Setting range Rated output current - Derating - Derating - Signaling contact "DC o. k." Remote On/Off	(at 115/230 V) 50/60 Hz			85264 V AC	85264 V AC	85264 V AC
Rated line frequency Rated input current - Inrush current - Inrush current - Recommended miniature circuit breaker Rated output voltage - Tolerance - Setting range Rated output current - Setting range Rated output current - Setting range - Setting range Rated output current - Setting range - Sett	50/60 Hz	(at 115/230 V)	> 15 ms	> 15 ms	> 15 ms	> 15 ms
Rated input current - Inrush current ¹⁾ - Recommended miniature circuit breaker Rated output voltage - Tolerance - Setting range - Sett		(40.1.15/250.1)	(at 115/230 V)	(at 115/230 V)	(at 115/230 V)	(at 115/230 V)
Rated input current - Inrush current ¹⁾ - Recommended miniature circuit breaker Rated output voltage - Tolerance - Setting range - Sett	1.1-0.7 A	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz
- Inrush current ¹⁾ < 60 A - Recommended miniature circuit breaker Rated output voltage 12 V DC - Tolerance ± 2% - Setting range 1114 V DC Rated output current 3 A - Derating from +50 °C (2.5 %/K) Efficiency at rated values, approx. Signaling contact "DC o. k." No Remote On/Off No Parallel switching Yes Electronic short-circuit protection Yes, restart Radio interference suppression (EN 55022) Supply harmonics limitation (EN 61000-3-2) Degree of protection [P20 (EN 60529) Ambient temperature -10+70 °C		1.5–1.0 A	2.0-1.1 A	2.0–1.1 A	3.1–2.0 A	4.0–2.0 A
- Recommended miniature circuit breaker Rated output voltage 12 V DC - Tolerance ± 2% - Setting range 1114 V DC Rated output current 3 A - Derating from +50 °C (2.5 %/K) Efficiency at rated values, approx. Signaling contact "DC o. k." No Remote On/Off No Parallel switching Yes Electronic short-circuit protection Yes, restart Radio interference suppression (EN 55022) Supply harmonics limitation (EN 61000-3-2) Degree of protection IP20 (EN 60529) Ambient temperature −10+70 °C	< 60 A	< 60 A	< 75 A	< 75 A	< 75 A	< 60 A
- Tolerance ± 2 % - Setting range 1114 V DC Rated output current 3 A - Derating from +50 °C (2.5 %/K) Efficiency at rated values, approx. Signaling contact "DC o. k." No Remote On/Off No Parallel switching Yes Electronic short-circuit protection Yes, restart Radio interference suppression (EN 55022) Supply harmonics limitation (EN 61000-3-2) Degree of protection IP20 (EN 60529) Ambient temperature −10+70 °C	characteristic B					
- Setting range 1114 V DC Rated output current 3 A - Derating from +50 °C (2.5 %/K) Efficiency at rated values, approx. Signaling contact "DC o. k." No Remote On/Off No Parallel switching Yes Electronic short-circuit protection Yes, restart Radio interference suppression (EN 55022) Supply harmonics limitation (EN 61000-3-2) Degree of protection IP20 (EN 60529) Ambient temperature −10+70 °C	24 V DC	24 V DC	24 V DC	12 V DC	24 V DC	24 V DC
Rated output current 3 A - Derating from +50 °C (2.5 %/K) Efficiency at rated values, 84% approx. Signaling contact "DC o. k." No Remote On/Off No Parallel switching Yes Electronic short-circuit protection Yes, restart Radio interference suppression (EN 55022) Supply harmonics limitation (EN 61000-3-2) Degree of protection IP20 (EN 60529) Ambient temperature -10+70 °C	± 2%	± 2%	± 2%	± 2 %	± 2 %	± 2 %
- Derating from +50 °C (2.5 %/K) Efficiency at rated values, 84 % approx. Signaling contact "DC o. k." No Remote On/Off No Parallel switching Yes Electronic short-circuit protection Yes, restart Radio interference suppression (EN 55022) Supply harmonics limitation (EN 61000-3-2) Degree of protection IP20 (EN 60529) Ambient temperature −10+70 °C	2228 V DC	2228 V DC	2228 V DC	1114 V DC	2228 V DC	2228 V DC
Efficiency at rated values, approx. Signaling contact "DC o. k." No Remote On/Off No Parallel switching Yes Electronic short-circuit protection Yes, restart Radio interference suppression (EN 55022) Supply harmonics limitation Not applicable (EN 61000-3-2) Degree of protection IP20 (EN 60529) Ambient temperature -10+70 °C	2.1 A	3.1 A	4.1 A	8.3 A	6.2 A	12.5 A
approx. Signaling contact "DC o. k." No Remote On/Off No Parallel switching Yes Electronic short-circuit protection Yes, restart Radio interference suppression Class B (EN 55022) Supply harmonics limitation Not applicable (EN 61000-3-2) Degree of protection IP20 (EN 60529) Ambient temperature -10+70 °C	from +50 °C (2.5 %/K)	from +50 °C (2.5 %/K)	from +50 °C (2.5 %/K)	from +50 °C (2.5 %/K)	from +50 °C (2.5 %/K)	from +50 °C (2.5 %/K)
Remote On/Off No Parallel switching Yes Electronic short-circuit protection Yes, restart Radio interference suppression (EN 55022) Supply harmonics limitation Not applicable (EN 61000-3-2) Degree of protection IP20 (EN 60529) Ambient temperature -10+70 °C	86%	86%	86%	84%	86%	86%
Parallel switching Yes Electronic short-circuit protection Yes, restart Radio interference suppression Class B (EN 55022) Supply harmonics limitation Not applicable (EN 61000-3-2) Degree of protection IP20 (EN 60529) Ambient temperature -10+70 °C	No	No	No	No	No	No
Electronic short-circuit protection Yes, restart Radio interference suppression Class B (EN 55022) Supply harmonics limitation Not applicable (EN 61000-3-2) Degree of protection IP20 (EN 60529) Ambient temperature -10+70 °C	No	No	No	No	No	No
Radio interference suppression (EN 55022) Supply harmonics limitation (EN 61000-3-2) Degree of protection (EN 60529) Ambient temperature —10+70 °C	Yes	Yes	Yes	Yes	Yes	Yes
(EN 55022) Supply harmonics limitation (EN 61000-3-2) Degree of protection (EN 60529) Ambient temperature (EN 5002)	Yes, restart	Yes, restart	Yes, restart	Yes, restart	Yes, restart	Yes, restart
(EN 61000-3-2) Degree of protection (EN 60529) Ambient temperature -10+70 °C	Class B	Class B	Class B	Class B	Class B	Class B
(EN 60529) Ambient temperature –10+70 °C	Not applicable	Yes	Yes	Yes	No	Yes
the state of the s	IP20	IP20	IP20	IP20	IP20	IP20
	−10+70 °C	−10+70 °C	−10+70 °C	−10+70 °C	−10+70 °C	−10+70 °C
Installation Wall mounting, variable inst						
Dimensions (W x H x D) in mm 97 x 98 x 38	stallation position	97 x 128 x 38	97 x 158 x 38	97 x 158 x 38	97 x 178 x 38	105 x 199 x 41
Weight approx. 0.37 kg	stallation position 97 x 128 x 38	0.37 kg	0.50 kg	0.57 kg	0.55 kg	0.81 kg
Certification CE, cULu, cURus		CE, cULus, cURus	CE, cULus, cURus	CE, cULus, cURus	CE, cULus, cURus	CE, cULus, cURus

¹⁾ Inrush current can be limited by a SITOP inrush current limiter: 6EP4683-6LB00-0AY0 (max. 5 A, 100–240 V AC).

Technical data applies at rated input voltage and ambient temperature of +25°C (unless otherwise specified).



¹⁾ Inrush current can be limited by a SITOP inrush current limiter: 6EP4683-6LB00-0AY0 (max. 5 A, 100–240 V AC) or 6EP1967-2AA00 (max. 10 A, 100–480 V AC, 1 unit per phase required).

²⁾ Via analog voltage signal 0....2.5 V

Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

SITOP expansion modules to increase system availability











SITOP RED1200 red SEP4346-7RB00-0AX0 2 V, 24 V, 48 V DC 058 V DC	dundancy module 6EP4347-7RB00-0AX0 12 V. 24 V. 48 V DC	Redundancy 6EP1964-2BA00	SITOP PSE202U redundancy modul 6EP1962-2BA00	2	
SEP4346-7RB00-0AX0 2 V, 24 V, 48 V DC	6EP4347-7RB00-0AX0		•	е	
2 V, 24 V, 48 V DC		6EP1964-2BA00	6ED1062 2DA00		
	12 V 24 V 48 V DC		UEF 1902-ZBAUU	6EP1961-3BA21	
	1058 V DC	24 V DC 1929 V DC	24 V DC 1929 V DC	24 V DC 2428.8 V DC	
	g. for series connection to increase				
R V power supplies with output currents up to 10 A or one 20-A power supply per redundancy	Decoupling of two 12 V to 48 V power supplies with output currents up to 20 A or one 40-A power supply per redundancy module	Decoupling of two 24-V power supplies up to 5 A or one 10-A power supply per redundancy module	Decoupling and limitation of the output to Class-2 limit (100 VA) of two 24-V power supplies 5 to 40 A	Decoupling of two 24-V power supplies 5 A to 20 A or one 40-A power supply per redundancy module	
20 A (total output current)	40 A (total output current)	10 A (total output current)	3.5 A ¹⁾	40 A (total output current)	
200 V DC	200 V DC	52 V DC	52 V DC	52 V DC	
97.5 %	97.5 %	97 %	95 %	97%	
Class B	Class B	Class B	Class B	Class B	
IP20	IP20	IP20	IP20	IP20	
Push-in	Push-in	Screw terminals	Screw terminals	Screw terminals	
-30+70 °C	−30+70 °C	−20+70 °C	−20+70 °C	−25+60 °C	
35 x 135 x 125	45 x 135 x 125	30 x 80 x 100	30 x 80 x 100	70 x 125 x 125	
).35 kg	0.35 kg	0.125 kg	0.125 kg	0.5 kg	
CE, cULus, CB, ATEX, IECex, CCC, in DNV GL, ABS	preparation: cCSAus Class1 div2,	CE, cULus	CE, cULus, NEC Class 2	CE, cULus, cCSAus Class I Div 2, ATEX, IECEx, CCC, DNV GL, ABS	
10000000000000000000000000000000000000	atput voltages from 12 to 48 V, e.g. Itage to up to 96 V or parallel conpplies to enhance performance. Secoupling of two 12 V to 8 V power supplies with output rrents up to 10 A or one 20-A ower supply per redundancy odule O A (total output current) O V DC 7.5 % ass B 120 15h-in 160+70 °C 15 x 135 x 125 35 kg 15, cULus, CB, ATEX, IECex, CCC, in	atput voltages from 12 to 48 V, e.g. for series connection to increase cltage to up to 96 V or parallel connection of more than 2 power pplies to enhance performance. Becoupling of two 12 V to 8 V power supplies with output trents up to 10 A or one 20-A power supply per redundancy odule 9 A (total output current) 40 A (total output current) 50 V DC 55 % 97.5 % Class B 120 1P20 1P20 1P20 1P20 1P20 1P20 1P20	switching threshold adjustable between the performance and the performance and the performance are coupling of two 12 V to the power supplies with output arrents up to 10 A or one 20-A power supply per redundancy and the power supply per redundan	switching threshold adjustable between 20 and 25 V DC ltage to up to 96 V or parallel connection of more than 2 power pplies to enhance performance. Secoupling of two 12 V to 84 V power supplies with output currents up to 10 A or one 20-A power supply per redundancy module A (total output current) B (Lass B) Class B Cla	

 $^{1)}$ Max. 8 A summation current in fault case in accordance with NEC Class 2 Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

	new!	new!		new!	new!					
	Elim - All			THE THE	M M Manager M M		0	G CDB	(3) (3)	CIB
Technical data						onitoring				
SITOP	SITOP SEL1200 se characteristic	electivity module wit	h switching	SITOP SEL1400 se characteristic	electivity module wit	h current limiting	SITOP PSE200U se with current limit and common sign	ing characteristic	SITOP PSE200U se with current limit and single-chann	ing characteristic
Article No.	6EP4437-7FB00- 3CX0	6EP4437-7FB00- 3DX0	6EP4438-7FB00- 3DX0	6EP4437-7EB00- 3CX0	6EP4437-7EB00- 3DX0	6EP4438-7EB00- 3DX0	6EP1961-2BA11	6EP1961-2BA21	6EP1961-2BA31	6EP1961-2BA4
Article No. with NEC Class 2							6EP1961-2BA51		6EP1961-2BA61	
Rated input voltage/range	24 V DC/20.430	V DC		24 V DC/20.430	V DC		24 V DC/2230 V I	DC	24 V DC/2230 V	DC
Brief product description	Module for distribution for all power supplemental for all power supplement		over up to four or eigh	nt load circuits and the	eir monitoring for over	load; selective shutdo	wn of faulty load circu	its, rated current indivi	idually adjustable; univ	versal use
Switch-off characteristic	Switching – for sta on overcurrent	Switching – for standard protection. Release time depending on overcurrent or overcurrent or overcurrent shutdown. Voltage dip below 20 V not possible, therefore also suitable for loads that do not meet the PLC standard								reshold value, ther
Status indication per output	3-color LED: green	- connected, yellow -	- manually disconnect	ted, red – disconnecte	d due to overcurrent					
Signal outputs	•	Diagnostics interface for common signaling or single-channel diagnostics. Analysis of single-channel diagnostics via SIMATIC S7 function block: current, set current threshold value, status (on/off), reason for disconnection (if applicable) measuring points for current value per output (1 V = 1 A) block. Voltage measuring points for current value per output (1 V = 1 A)							SIMATIC S7-funct	
Reset, outputs switched on/off	Remote reset with	24-V signal. Reset and	each output switched	d on/off via push butto	n					
Individual load circuits switched on sequentially	Load-optimized (p	revious output less th	an set rated value) +	25 ms, + 200 ms, or -	+ 500 ms		0 ms (simultaneou set rated value)	sly), 25 ms,100 ms or	load-optimized (previ	ous output less th
Rated output current	4 x 10 A	8 x 5 A	8 x 10 A	4 x 10 A	8 x 5 A	8 x 10 A	4 x 3 A	4 x 10 A	4 x 3 A	4 x 10 A
– Setting range	210 A	15 A	210 A	210 A	15 A	210 A	0,53 A	310 A	0,53 A	310 A
Efficiency at rated values, approx.	typ. 98%	typ. 98%	typ. 98%	typ. 98%	typ. 98%	typ. 98%	97%	99%	97%	99%
Parallel switching of 2 outputs	Yes (max. 15 A)	Yes (max. 7.5 A)	Yes (max. 15 A)	Yes (max. 15 A)	Yes (max. 7.5 A)	Yes (max. 15 A)	No	No	No	No
Electronic short-circuit protection	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Radio interference suppression (EN 55022)	Class B	Class B	Class B	Class B	Class B	Class B	Class B	Class B	Class B	Class B
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20	IP20	IP20	IP20	IP20	IP20	IP20
Terminals	Push-in	Push-in	Push-in	Push-in	Push-in	Push-in	Screw terminals	Screw terminals	Screw terminals	Screw termina
Ambient temperature	−25+70 °C	−25+70 °C	−25+70 °C	−25+70 °C	−25+70 °C	−25+70 °C	−25+60 °C	−25+60 °C	−25+60 °C	−25+60 °C
Dimensions (W x H x D) in mm	45 x 135 x 125	45 x 135 x 125	45 x 135 x 125	45 x 135 x 125	45 x 135 x 125	45 x 135 x 125	72 x 80 x 72	72 x 80 x 72	72 x 80 x 72	72 x 80 x 72
Weight approx.	0.3 kg	0.3 kg	0.3 kg	0.3 kg	0.3 kg	0.3 kg	0.2 kg	0.2 kg	0.2 kg	0.2 kg
Certification	CE, UL, cULus, CB,	CSA, ATEX, IECEx, CC	C, in preparation: cCS	SAus Class I Div 2, GL	und ABS		CE, UL, cURus, CB, BA51/6EP1961-2BA	cULus Class I Div 2, AT A61: NEC Class 2	EX, IECEx, CCC, DNV	GL, ABS, 6EP1961

Technical data applies at rated input voltage and ambient temperature of +25°C (unless otherwise specified)

SITOP expansion modules to increase system availability

Uninterruptible power supplies – SITOP UPS500 maintenance-free DC UPS with capacitor technology









Technical data	Mains buffering u	Mains buffering up to the minutes range			
SITOP	Buffer module ¹⁾ SITOP PSE201U	Buffer module SITOP BUF1200	UPS500S-basic u	nit 15 A	UPS501S – expansion module
Buffer time/Energy	200 ms/40 A	300 ms/40 A	2.5 kWs	5 kWs	5 kWs
Article No.	6EP1961-3BA01	6EP4231-7HB00-0AX0	6EP1933-2EC41	6EP1933-2EC51	6EP1935-5PG01
Input voltage	24 V DC/2428.8 V DC	24 V DC/2030 V DC	24 V DC, 2229 V	, infeed from SITOP 24 V	Infeed from basic unit
Rated input current	Module for buffering during short	Module for buffering during short	15.2 A + approx. 2	2.3 A in charging mode	Description: expansion module for extending
Rated output voltage	power failures; parallel connection at output of 24-V power supplies ¹⁾ .	power failures; parallel connection at output of 24-V power supplies.	In buffer and norm	nal mode 24 V DC ± 3 %	the buffering time, up to three units can be switched in parallel with one UPS500S basic
Rated output current	Buffering time 200 ms at 40 A up to 1.6 s at 5 A load current;	Buffering time 300 ms at 40 A up to 2.4 s at 5 A load current;	15 A, charging cur or 2 A selectable	rrent 1 A (factory setting)	unit
Efficiency at rated values, approx.	multiplication possible through parallel connection; maximum	multiplication possible through parallel connection	97.5%		
Overload and short-circuit protection	buffering time 10 s		Electronic, automatic restart		
Parallel switching	Yes	Yes	No		Yes, up to three units
Radio interference suppression (EN 55022)	Class B	Class B	Class B	Class B	Class B
Degree of protection (EN 60529)	IP20	IP20	IP20	IP20	IP20
Ambient temperature	0+60 °C	−30+70 °C	0+60 °C	0+60 °C	0+60 °C
Dimensions (W x H x D) in mm	70 x 125 x 125	70 x 135 x 155	120 x 125 x 125	120 x 125 x 125	70 x 125 x 125
Weight approx.	1.2 kg	1.5 kg	1.0 kg	1.0 kg	0.7 kg
Certification	CE, UL, CSA, ATEX, CCC, UL Class I Div 2, DNV GL, ABS	CE, cULus, CB, SEMI F47, ATEX, CCC, in preparation: cCSAus Class I Div 2, DNV GL, ABS	CE, cULus, CB, ATEX, CCC, cCSAus Class I Div 2, DNV GL, ABS		

¹⁾ Can be combined with SITOP PSU8200, PSU6200 and SITOP smart 24-V power supplies (except 6EP1 336-2BA10) Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Buffering times and charging times SITOP UPS500



SITOP UPS500S/501S configurations								
Basic unit	2.5 kWs	5 kWs	2.5 kWs	5 kWs	2.5 kWs	5 kWs	2.5 kWs	5 kWs
Expansion modules	_	-	1 x 5 kWs	1 x 5 kWs	2 x 5 kWs	2 x 5 kWs	3 x 5 kWs	3 x 5 kWs
Total energy	2.5 kWs	5 kWs	7.5 kWs	10 kWs	12.5 kWs	15 kWs	17.5 kWs	20 kWs

Buffering times								
Load current								
0.5 A	134 s	236 s	390 s	478 s	632 s	748 s	851 s	1,007 s
0.8 A	90 s	167 s	266 s	346 s	440 s	527 s	580 s	706 s
1 A	75 s	138 s	219 s	296 s	365 s	414 s	490 s	572 s
2 A	38 s	76 s	122 s	156 s	203 s	230 s	265 s	306 s
3 A	26 s	52 s	82 s	106 s	136 s	159 s	186 s	213 s
4 A	19 s	39 s	61 s	81 s	101 s	120 s	139 s	160 s
5 A	15 s	31 s	49 s	65 s	81 s	95 s	111 s	130 s
6 A	12 s	26 s	40 s	55 s	67 s	80 s	94 s	106 s
7 A	10 s	21 s	34 s	47 s	58 s	69 s	81 s	82 s
8 A	8 s	18 s	29 s	40 s	50 s	59 s	69 s	79 s
10 A	6 s	15 s	23 s	32 s	39 s	47 s	54 s	62 s
12 A	4 s	12 s	19 s	26 s	32 s	38 s	44 s	52 s
15 A	3 s	9 s	14 s	20 s	25 s	30 s	35 s	40 s

Charging times								
Charging current								
2 A	54 s	120 s	158 s	223 s	263 s	318 s	355 s	417 s
1 A	110 s	205 s	311 s	425 s	503 s	625 s	695 s	816 s

Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

Uninterruptible power supplies SITOP DC UPS with battery modules for bridging longer power failures










echnical data			Mains buffering up to the hou	rs range	
ITOP	UPS1600	UPS1600	UPS1600	Battery module UPS1100	Battery module UPS1100
nergy storage				Lead storage batteries	Lead storage batteries
utput voltage/current or charge	24 V/10 A	24 V/20 A	24 V/40 A	24 V/1.2 Ah	24 V/3.2 Ah
				for UPS1600 10 A	for UPS1600 10 A and 20 A
rticle No.	6EP4134-3AB00-0AY0	6EP4136-3AB00-0AY0	6EP4137-3AB00-0AY0	6EP4131-0GB00-0AY0	6EP4133-0GB00-0AY0
with USB interface	6EP4134-3AB00-1AY0	6EP4136-3AB00-1AY0	6EP4137-3AB00-1AY0		
with Ethernet/PROFINET interface	6EP4134-3AB00-2AY0	6EP4136-3AB00-2AY0	6EP4137-3AB00-2AY0		
nput voltage	24 V DC, 2229 V, infeed	ed from 24-V SITOP power supply Recommended end-of-charge voltage (set automatically by SITOP UPS1600)			
ated input current	approx. 14 A at max. charging current (3 A)	approx. 25 A at max. charging (4 A)	approx. 46 A at max. charging (5 A)	Charging current max. 0.3 A	Charging current max. 0.9 A
ated output voltage	24 V DC (upstream SITOP	device or battery), charging	y voltage: 27.0 V	24 V DC, 2227.0 V DC (no-load of	operation)
ated output current	10 A, charging current	20 A, charging current	40 A, charging current max. 5 A	10 A	20 A
Overload behavior (power boost for 30 ms)	30 A	60 A	120 A		
Overload behavior (extra power for 5 s/min)	15 A	30 A	60 A		
fficiency at rated values, approx.	> 97.7 %	> 98.2 %	> 98.8 %	Not applicable	Not applicable
verload and shortcircuit protection	Yes, restart in normal mod	de		Installed battery fuse: 15 A/32 V	Installed battery fuse: 25 A/32 \
arallel switching	No	No	No	Yes, up to six units	Yes, up to six units
adio interference suppression	Class B (EN 55022)	Class B (EN 55022)	Class B (EN 55022)	-	_
egree of protection (EN 60529)	IP20	IP20	IP20	IP20	IP20
mbient temperature (derating from +60 °C)	−25+70 °C	−25+70 °C	−25+70 °C	−15+50 °C	−15+50 °C
nstallation	DIN rail	DIN rail	DIN rail	DIN rail or wall mounting	DIN rail or wall mounting
imensions (W x H x D) in mm	50 x 125 x 125	50 x 125 x 125	70 x 125 x 150	89 x 130 x 107	190 x 169 x 79
leight approx.	0.38/0.4/0.44 kg	0.39/0.41/0.45 kg	0.65/0.65/0.7 kg	1.9 kg	3.8 kg
ertification	CE, cULus, CB, ATEX, IECEX DNV GL, ABS	c, CCC, cCSAus Class I Div 2,	CE, cULus, CB, ATEX, IECEx, CCC, cCSAus Class I Div 2, DNV GL, ABS	CE, cURus, CB, ATEX, IECEx, CCC, cCSAus Class I Div 2, DNV GL, ABS	CE, cURus, CB, ATEX, IECEX, CCC, cCSAus Class I Div 2, DNV GL, AB

Battery module selection table: buffer times and service life



	- In				la la	
UPS1100 battery module	1.2 Ah	3.2 Ah	7 Ah	12 Ah	2.5 Ah	5 Ah
Load current		,	Bufferin	g times ¹⁾		
1 A	27 min	2 h	5 h	8 h 30 min	1 h 30 min	4 h
2 A	14 min	1 h	2 h 40 min	4 h 30 min	50 min	2 h 10 min
3 A	10 min	45 min	1 h 50 min	3 h 10 min	36 min	1 h 30 min
4 A	7 min 50 s	34 min	1 h 20 min	2 h 30 min	26 min	1 h 10 min
6 A	4 min 40 s	21 min	48 min	1 h 30 min	15 min	48 min
8 A	3 min	15 min	34 min	1 h	11 min	37 min
10 A	1 min 30 s	9 min 30 s	21 min	42 min	6 min 40 s	26 min
12 A	-	8 min 10 s	19 min	37 min	5 min 40 s	23 min
14 A	_	6 min 50 s	16 min	32 min	4 min 40 s	21 min
16 A	-	5 min 30 s	13 min	27 min	3 min 40 s	18 min
20 A	_	2 min 50 s	7 min 50 s	17 min	1 min 40 s	13 min
30 A	-	-	3 min 50 s	10 min	3 min 20 s, 2x ²⁾	17 min, 2x ²⁾
40 A	-	-	1 min 40 s	5 min 30 s	1 min 40 s, 2x ²⁾	13 min, 2x ²⁾
Ambient temperature	Approxim			to 80% of th ttery tempe		capacity),
+20 °C	4 years	4 years	4 years	4 years	10 years	15 years
+30 °C	2 years	2 years	2 years	2 years	7 years	10 years
+40 °C	1 year	1 year	1 year	1 year	3 years	9 years
+50 °C	0.5 years	0.5 years	0.5 years	0.5 years	1.5 years	2 years
+60 °C					1 year	

¹⁾ Buffer time determination is based on the discharging time of new and completely charged battery modules with a minimum battery temperature of +25 °C until DC UPS (19 V) turns off.

The SITOP Selection Tool can be used to determine buffer times for additional temperatures and buffer voltages: siemens.com/tst-powersupply 2) With two parallel connected UPS1100 battery modules and UPS1600 40 A

Find out more:

siemens.com/sitop

Additional information on SITOP:

- > TIA Selection Tool: siemens.com/tst-powersupply
- Operating instructions as download: siemens.com/sitop/manuals
- Request CAx data via the CAx download manager: siemens.com/cax

More about SITOP on YouTube




Article No.: DIPA-B10072-02-7600

Dispo 10001

WS 01211.5

Printed in Germany

© Siemens 2021



Published by Siemens AG

Digital Industries Process Automation Östliche Rheinbrückenstr. 50 76187 Karlsruhe, Germany

For the U.S. published by Siemens Industry Inc

100 Technology Drive Alpharetta, GA 30005 United States twitter.com/siemensindustry youtube.com/siemens

Subject to changes and errors. The information provided in this brochure contains descriptions or performance characteristics which, in case of actual use, do not always apply as described or which may change as a result of further development of the products. The desired performance characteristics are only binding if expressly agreed in the contract. Availability and technical specifications are subject to change without notice.

All product designations may be trademarks or product names of Siemens AG or supplier companies, the use of which by third parties for their own purposes may violate the rights of the owners.

Industrial Security

Siemens provides automation and drive products with industrial-security functions that support the secure operation of plants or machines. They are an important component in a holistic industrial-security concept. With this in mind, our products undergo continuous development. We therefore recommend that you keep yourself informed with respect to our product updates and that you use only the latest versions. Please find further information on this subject at automation.siemens.com/support.

You may also register for a product-specific newsletter at this address.

To ensure the secure operation of a plant or machine it is also necessary to take suitable preventive action (e.g., cell protection concept) and to integrate the automation and drive components into a state-of-the-art holistic industrial-security concept for the entire plant or machine. Any third-party products that may be in use must also be taken into account. Please find further information at siemens.com/industrialsecurity.