


Overview



SITRANS LR200 is a 2-wire, 6 GHz pulse radar level transmitter for continuous monitoring of liquids and slurries in process vessels including high temperature, pressure, agitation, and turbulence to a range of 20 m (65 ft).

Benefits

- Graphical local user interface (LUI) makes operation simple with plug-and-play setup using the intuitive Quick Start Wizard
- LUI displays echo profiles for diagnostic support
- Communication using HART or PROFIBUS PA
- Process Intelligence signal processing for improved measurement reliability and Auto False-Echo Suppression of fixed obstructions
- Programming using infrared Intrinsically Safe handheld programmer or SIMATIC PDM

Application

SITRANS LR200's unique design allows safe and simple programming using the Intrinsically Safe handheld programmer without having to open the instrument's lid. It also features a built-in alphanumeric display in four languages.

The SITRANS LR200 has a standard Uni-Construction polypropylene rod antenna that offers excellent chemical resistance and is hermetically sealed. The Uni-Construction antenna features an internal, integrated shield that eliminates vessel nozzle interference.

Startup is easy with as few as two parameters for basic operation. Installation is simplified as the electronics are mounted on a rotating head that swivels, allowing the instrument to line up with conduit or wiring connections or simply to adjust the position for easy viewing. SITRANS LR200 features Process Intelligence signal-processing technology for superior reliability.

- Key Applications: liquid process vessels with agitators, vaporous liquids, high temperatures, asphalt


Configuration

Installation


Min. 300 mm (1 ft) for every 3 m (10 ft) of vessel wall.

Note:


- Beam angle is the width of the cone where the energy density is half of the peak energy density.
- Beam angle for horn antenna dependent on horn size
- The peak energy density is directly in front of and in line with the rod antenna.
- There is a signal transmitted outside of the beam angle; therefore false targets may be detected.




Mounting unit on vessel



Mounting unit on stilling well



Mounting on a nozzle



SITRANS LR200 installation, dimensions in mm (inch)

Level measurement

Continuous level measurement
Radar level transmitters

SITRANS LR200

Integration



SITRANS LR200 with flange adapter for connection to optional antennas.



Horn with waveguide extension. Used for high temperature isolation, long standpipes, and clearing tank obstructions.



Flat faced flange connection with PTFE rod antenna.



Shielded rod antenna with a stainless steel shield eliminates standpipe interference. Various lengths available.

Antenna configurations for SITRANS LR200

Antenna types	Flat Faced Flange with Rod	Shielded Rod	Horn (4", 6", 8" sizes available)
Connection type	Flat faced flange nominal pipe sizes 50, 80, 100, 150 mm (2, 3, 4, 6 inch)	Threaded 2" NPT, R 2" (BSPT), G 2" (BSPP) or flat faced flange nominal pipe sizes 80, 100 mm (3, 4 inch)	Flat faced flange nominal pipe sizes 50, 80, 100, 150 mm (2, 3, 4, 6 inch)
Wetted parts	PTFE	PTFE, 316L stainless steel, FKM O-ring	316L stainless steel PTFE, FKM O-ring
Extensions	50 or 100 mm (2 or 4 inch) PTFE or UHMW-PE	100, 150, 200 or 250 mm (4, 6, 8 or 10 inch) standard shield length	Use waveguide for extensions to 6 m (20 ft) long
Dielectric constant	> 3	> 3	> 3
Insertion length (max.)	41 cm (16.3 inch)	Variable	Variable with extension
Purging option (liquid or gas)	No	No	Yes
Sliding waveguide option for digesters¹⁾	Yes	No	Yes
Weight²⁾	6.5 kg (14.3 lb)	5.0 kg (11 lb)	7.5 kg (16.5 lb)

¹⁾ Maximum pressure 0.5 bar g at 60 °C (7.25 psi g at 140 °F)

²⁾ Not including extensions, includes SITRANS LR200 and smallest process connection

Technical specifications

Mode of operation		Power supply	
Measuring principle	Radar level measurement	4 ... 20 mA/HART	Nominal 24 V DC (max. 30 V DC) with max. 550 Ω
Frequency	C-band, approx. 6 GHz	<ul style="list-style-type: none"> General Purpose, Non-incendive, Intrinsically Safe Flame proof, Increased safety, Explosion proof 	
Measuring range	0.3 ... 20 m (1.0 ... 65 ft)	PROFIBUS PA	Nominal 24 V DC (max. 30 V DC) with max. 250 Ω
Output		<ul style="list-style-type: none"> 10.5 mA Per IEC 61158-2 	
Analog output	4 ... 20 mA	Certificates and approvals	
Accuracy	± 0.02 mA	General	cCSA _{US} , CE, UKCA, FM, RCM
Span	Proportional or inversely proportional	Marine	<ul style="list-style-type: none"> Lloyd's Register of Shipping ABS Type Approval
Communications	HART Optional: PROFIBUS PA (Profile 3.0, Class B)	Radio	FCC, Industry Canada, and European (RED), RCM
Fail-safe	Programmable as high, low or hold (Loss of Echo)	Hazardous	INMETRO Ex ia IIC T4 Ga CSA/FM, Class I, Div. 1, Groups A, B, C, D; Class II, Div. 1, Groups E, F, G; Class III, T4
Performance (according to reference conditions IEC60770-1)		<ul style="list-style-type: none"> Intrinsically Safe (Brazil) Explosion Proof (Canada/USA) 	
From end of antenna to 600 mm	40 mm (1.57 inch)	<ul style="list-style-type: none"> Intrinsically Safe (Canada/USA) 	CSA/FM, Class I, Div. 1, Groups A, B, C, D; Class II, Div. 1, Groups E, F, G; Class III, T4
Remainder of range	10 mm (0.4 inch) or 0.1 % of span (whichever is greater)	<ul style="list-style-type: none"> Non-incendive (USA) 	FM, Class I, Div. 2, Groups A, B, C, D, T5
Rated operating conditions		<ul style="list-style-type: none"> Flame Proof/Increased Safety (China) Flame Proof (Europe) Flame Proof (UK) Increased Safety (Europe) Increased Safety (UK) 	NEPSI Ex d mb ia IIC T4/ Ex e mb ia IIC T4
Installation conditions	Indoor/outdoor	<ul style="list-style-type: none"> Increased Safety (Europe) Intrinsically Safe (Europe) Intrinsically Safe (UK) Intrinsically Safe (International) Intrinsically Safe (Russia/Kazakhstan) 	ATEX II 1/2 G Ex d mb ia IIC T4 Ga/Gb
• Location		<ul style="list-style-type: none"> ATEX II 1/2 G Ex d mb ia IIC T4 Ga/Gb UKEX II 1/2 G Ex d mb ia IIC T4 Ga/Gb ATEX II 1/2 G Ex e mb ia IIC T4 Ga/Gb UKEX II 1/2 G Ex e mb ia IIC T4 Ga/Gb ATEX II 1G Ex ia IIC T4 Ga UKEX II 1G Ex ia IIC T4 Ga IECEx Ex ia IIC T4 Ga EAC Ex ia 	
Ambient conditions (enclosure)		<ul style="list-style-type: none"> ATEX II 1/2 G Ex d mb ia IIC T4 Ga/Gb UKEX II 1/2 G Ex d mb ia IIC T4 Ga/Gb ATEX II 1/2 G Ex e mb ia IIC T4 Ga/Gb UKEX II 1/2 G Ex e mb ia IIC T4 Ga/Gb ATEX II 1G Ex ia IIC T4 Ga UKEX II 1G Ex ia IIC T4 Ga IECEx Ex ia IIC T4 Ga EAC Ex ia 	
• Ambient temperature		-40 ... +80 °C (-40 ... +176 °F)	<ul style="list-style-type: none"> ATEX II 1G Ex ia IIC T4 Ga UKEX II 1G Ex ia IIC T4 Ga IECEx Ex ia IIC T4 Ga EAC Ex ia
• Storage temperature		-40 ... +80 °C (-40 ... +176 °F)	
• Installation category	I		
• Pollution degree	4		
Medium conditions			
Dielectric constant ϵ_r	$\epsilon_r > 1.6$ (for $\epsilon_r < 3$, use stillpipe)		
Vessel temperature and pressure	Varies with connection type; see Pressure/Temperature curves for more information		
Design		Programming	
Enclosure	Aluminum, polyester powder coated 2 x M20 x 1.5 or 2 x 1/2" NPT	Intrinsically Safe Siemens handheld programmer	Infrared receiver
• Material			
• Cable inlet		<ul style="list-style-type: none"> Approvals for handheld programmer 	IS model:
Degree of protection	Type 4X/NEMA 4X, Type 6/ NEMA 6, IP67, IP68		ATEX II 1 GD Ex ia op is IIC T4 Ga, ATEX II 1 GD Ex ia op is IIIC T135°C Da, Ta = -20°C to +50°C; UKEX II 1 GD Ex ia op is IIC T4 Ga, UKEX II 1 GD Ex ia op is IIIC T135°C Da, Ta = -20°C to +50°C; CSA/FM Class I, II, III, Div. 1, Groups A, B, C, D, E, G, T6, Ta = 50°C; IECEx SIR 09.0073
Weight	< 2.82 kg (6.21 lb) (polypropylene rod antenna)	Handheld communicator	HART communicator 375
Display (local)	Multi-segment alphanumeric liquid crystal with bar graph (representing level) available in four languages	PC	<ul style="list-style-type: none"> SIMATIC PDM AMS SITRANS DTM (for connecting to FDT such as PACTware or Fieldcare)
Antenna	Polypropylene rod, hermetically sealed construction, optional PTFE	Display (local)	Multi-segment alphanumeric liquid crystal with bar graph (representing level) available in four languages
• Material			
• Dimensions	Standard 100 mm (4 inch) shield for maximum 100 mm (4 inch) nozzle, or optional 250 mm (10 inch) long shield		
• Optional rods and horn	Refer to SITRANS LR200 Antennas for optional rods and horns		
Process connections	1 1/2" NPT [(Taper), ASME B1.20.1] R 1 1/2" [(BSPT), EN 10226], or G 1 1/2" [(BSPP), EN ISO 228-1] (polypropylene rod antenna)		
• Process connection			
• Flange connection	Refer to SITRANS LR200 Antennas for more connections		

Level measurement

Continuous level measurement
Radar level transmitters

SITRANS LR200

Selection and ordering data

Article No.

Order code

SITRANS LR200 Radar level transmitter with polypropylene rod

Continuous, non-contact, 20 m (66 ft) range, for liquids and slurries.

➤ Click on the Article No. for the online configuration in the PIA Life Cycle Portal.

Enclosure/Cable inlet

Aluminum, epoxy painted

2 x 1/2" NPT

2 x M20 x 1.5

Polypropylene antenna type - (Max. 3 Bar pressure and 80 °C)

1 1/2" NPT [(Taper), ASME B1.20.1],

c/w integral 100 mm shield

R 1 1/2" [(BSPT), EN 10226],

c/w integral 100 mm shield

G 1 1/2" [(BSPP), EN ISO 228-1],

c/w integral 100 mm shield

1 1/2" NPT [(Taper), ASME B1.20.1],

c/w integral 250 mm shield

R 1 1/2" [(BSPT), EN 10226],

c/w integral 250 mm shield

G 1 1/2" [(BSPP), EN ISO 228-1],

c/w integral 250 mm shield

Approvals

Ordinary Locations/General Purpose (Non-Ex), CE, UKCA, RED, RCM

Ordinary Locations/General Purpose (Non-Ex), CSA, FM, IC, FCC

Intrinsically Safe, CSA Class I, II, Div. 1,

Groups A, B, C, D, E, F, G, Industry Canada

Intrinsically Safe, FM Class I, II, Div. 1,

Groups A, B, C, D, E, F, G, FCC

Intrinsically Safe;

ATEX II 1G Ex ia IIC T4 Ga;

UKEX II 1G Ex ia IIC T4 Ga;

IECEx Ex ia IIC T4 Ga;

INMETRO Ex ia IIC T4 Ga, IP67/IP68;

EAC Ex 0Ex ia IIC T4 Ga X;

CE, UKCA, RED, RCM, EAC

Non incandive, FM Class I, Div. 2,

Groups A, B, C, D, FCC¹⁾

Increased Safety:

ATEX II 1/2G Ex eb mb ia IIC T4 Ga/Gb;

UKEX II 1/2G Ex eb mb ia IIC T4 Ga/Gb;

CE, UKCA, RED, RCM, EAC²⁾³⁾

Flameproof:

ATEX II 1/2G Ex db mb ia IIC T4 Ga/Gb;

UKEX II 1/2G Ex db mb ia IIC T4 Ga/Gb;

CE, UKCA, RED, RCM, EAC³⁾

Explosion Proof, CSA/FM Class I, II, III,

Groups A, B, C, D, E, F, G, Industry Canada,

FCC¹⁾³⁾

Communication/Output

PROFIBUS PA

4 ... 20 mA, HART, start-up at < 3.6 mA

¹⁾ Available with enclosure option 2 only.

²⁾ Available with enclosure option 3 only.

³⁾ Available with communication option 3 only.

7ML5422-

0

2

3

A

B

C

D

E

F

A

B

C

D

E

F

A

B

C

D

E

F

A

B

C

D

E

F

A

B

C

D

E

F

A

B

C

D

E

F

A

B

C

D

E

F

A

B

C

D

E

F

Further designs

Please add "-Z" to Article No. and specify Order code(s).

Stainless steel tag [69 x 50 mm (2.71 x 1.97 inch)]; Measuring-point number/identification (max. 27 characters); specify in plain text

Y15

Manufacturer's test certificate: M to DIN 55350, Part 18 and to ISO 9000

C11

Namur NE43 compliant, device preset to failsafe < 3.6 mA¹⁾

N07

Operating Instructions

All literature is available to download for free, in a range of languages, at

<http://www.siemens.com/processinstrumentation/documentation>

Accessories

Handheld programmer, Intrinsically safe, EEx ia

Article No.

7ML1930-1BK

HART modem/USB (for use with a PC and SIMATIC PDM)

7MF4997-1DB

One metallic cable gland M20 x 1.5, rated -40 ... +80 °C (-40 ... +176 °F), HART²⁾

7ML1930-1AP

One metallic cable gland M20 x 1.5, rated -40 ... +80 °C (-40 ... +176 °F), PROFIBUS PA²⁾

7ML1930-1AQ

One general purpose polymeric cable gland M20 x 1.5, rated -20 ... +80 °C (-40 ... +176 °F)

7ML1930-1AM

SITRANS RD100, loop powered display - see Chapter 7

7ML5741-.....-

SITRANS RD150, remote digital display for 4 ... 20 mA and HART devices - see Chapter 7

7ML5742-.....-

SITRANS RD200, universal input display with Modbus conversion - see Chapter 7

7ML5740-.....-

SITRANS RD300, dual line display with totalizer and linearization curve and Modbus conversion - see Chapter 7

7ML5744-.....-

For applicable back up point level switch - see point level measurement section

¹⁾ Available with communication option 3 only.

²⁾ Product shipped with plastic cable gland, rated to -20 °C. If -40 °C rating required, then metallic cable gland is recommended.

Selection and ordering data	Article No.	Article No.	
SITRANS LR200 Radar level transmitter with PTFE rod Continuous, non-contact, 20 m (66 ft) range, for liquids and slurries. Click on the Article No. for the online configuration in the PIA Life Cycle Portal.	7ML5423-	7ML5423-	
Antenna material (uses antenna adapter) PTFE, uses antenna adapter and additional process connection below	1	2 3	
Process connection (refer to Pressure/Temperature curves, page 4/259) Flanges (316L stainless steel) DN 50 PN 16, Type A, flat faced DN 80 PN 16, Type A, flat faced DN 100 PN 16, Type A, flat faced DN 150 PN 16, Type A, flat faced 2" ASME 150 lb, flat faced 3" ASME 150 lb, flat faced 4" ASME 150 lb, flat faced 6" ASME 150 lb, flat faced DN 50 PN 40, flat faced DN 80 PN 40, flat faced DN 100 PN 40, flat faced DN 150 PN 40, flat faced 2" ASME 300 lb, flat faced, available with Pressure rating option 1 only due to flange hole spacing 3" ASME 300 lb, flat faced 4" ASME 300 lb, flat faced 6" ASME 300 lb, flat faced JIS DN 50 10K JIS DN 80 10K JIS DN 100 10K JIS DN 150 10K (Note: Flange bolting patterns and facings dimensionally correspond to the applicable ASME B16.5, or EN 1092-1, or JIS B 2220 standard.) Threaded connection (316L stainless steel) 1½" NPT [(Taper), ASME B1.20.1] 2" NPT [(Taper), ASME B1.20.1] R 1½" [(BSPT), EN 10226] R 2" [(BSPT), EN 10226] G 1½" [(BSPP), EN ISO 228-1] G 2" [(BSPP), EN ISO 228-1]	A A B A C A D A F B G B H B J B A C B C C C D C F D G D H D J D A E B E C E D E L A M A L C M C L E M E	Enclosure/Cable inlet Aluminum, Epoxy painted 2 x ½" NPT 2 x M20 x 1.5 Communication/Output PROFIBUS PA 4 ... 20 mA, HART, start-up at < 3.6 mA Approvals Ordinary Locations/General Purpose (Non-Ex), CE, UKCA, RED, RCM Ordinary Locations/General Purpose (Non-Ex), CSA, FM, IC, FCC Intrinsically Safe, CSA Class I, II, Div. 1, Groups A, B, C, D, E, F, G, Industry Canada Intrinsically Safe, FM Class I, II, Div. 1, Groups A, B, C, D, E, F, G, FCC Intrinsically Safe; ATEX II 1G Ex ia IIC T4 Ga; UKEX II 1G Ex ia IIC T4 Ga; IECEx Ex ia IIC T4 Ga; INMETRO Ex ia IIC T4 Ga, IP67/IP68; EAC Ex 0Ex ia IIC T4 Ga X; CE, UKCA, RED, RCM, EAC Non incandive, FM Class I, Div. 2, Groups A, B, C, D, FCC ²⁾ Increased Safety: ATEX II 1/2G Ex eb mb ia IIC T4 Ga/Gb; UKEX II 1/2G Ex eb mb ia IIC T4 Ga/Gb; CE, UKCA, RED, RCM, EAC ²⁾³⁾ Flameproof: ATEX II 1/2G Ex db mb ia IIC T4 Ga/Gb; UKEX II 1/2G Ex db mb ia IIC T4 Ga/Gb; CE, UKCA, RED, RCM, EAC ³⁾ Explosion Proof, CSA/FM Class I, II, III, Groups A, B, C, D, E, F, G, Industry Canada, FCC ²⁾⁴⁾	B C B C D E F G H J 0 1
Antenna extensions or Inactive shield length No antenna extension 50 mm (2 inch) extension, PTFE 100 mm (4 inch) extension, PTFE 100 mm (4 inch) extension, 316L stainless steel shield ¹⁾ 150 mm (6 inch) extension, 316L stainless steel shield ¹⁾ 200 mm (8 inch) extension, 316L stainless steel shield ¹⁾ 250 mm (10 inch) extension, 316L stainless steel shield ¹⁾	0 1 2 3 4 5 6		
Process seal/gasket Integral Gasket, for flat faced flange process connections only, not for Antenna extension options 3 ... 6 FKM O-ring, not available for combination of flat faced flanges with Antenna extension options 0, 1 or 2	0 1		
		Pressure rating Rating per Pressure/Temperature curves in manual 0.5 bar g (7.25 psi g) maximum 1) Available with process connection options BA, CA, DA, GB, HB, JB, BC, CC, DC, GD, HD, JD, BE, CE, DE, MA, MC, ME only. 2) Available with enclosure option 2 only. 3) Available with enclosure option 3 only. 4) Available with communication option C only.	

Level measurement

Continuous level measurement
Radar level transmitters

SITRANS LR200

Selection and ordering data

Order code

Article No

Further designs

Please add "-Z" to Article No. and specify Order code(s).

Stainless steel tag [69 x 50 mm (2.71 x 1.97 inch)]:
Measuring-point number/identification
(max. 27 characters); specify in plain text

Y15

Manufacturer's test certificate: M to DIN 55350,
Part 18 and to ISO 9000

C11

Material inspection Certificate Type 3.1 per
EN 10204

C12

Namur NE43 compliant, device preset to failsafe
< 3.6 mA³)

N07

Operating Instructions

All literature is available to download for free, in a
range of languages, at

<http://www.siemens.com/processinstrumentation/documentation>

Accessories

Handheld programmer, Intrinsically safe, EEx ia

7ML1930-1BK

Antenna, rod, PTFE

7ML1830-1HC

Antenna extension, 50 mm (2 inch), PTFE

7ML1830-1CH

Antenna extension, 100 mm (4 inch), PTFE

7ML1830-1CG

HART modem / USB (for use with PC and
SIMATIC PDM)

7MF4997-1DB

Metallic cable gland M20 x 1.5,
rated -40 °C (-40 °F) ... 80 °C (176 °F),
HART (two are required)

7ML1930-1AP

Metallic cable gland M20 x 1.5,
rated -40 °C (-40 °F) ... 80 °C (176 °F),
PROFIBUS PA (two required)

7ML1930-1AQ

One General Purpose polymeric cable gland
M20 x 1.5, rating for -20 °C (-4°F) ... + 80 °C (176 °F)

7ML1930-1AM

SITRANS RD100, loop powered display -
see Chapter 7

7ML5741-.....-

SITRANS RD150, remote digital display for
4 ... 20 mA and HART devices - see Chapter 7

7ML5742-.....-

SITRANS RD200, universal input display with
Modbus conversion - see Chapter 7

7ML5740-.....-

SITRANS RD300, dual line display with totalizer and
linearization curve and Modbus conversion -
see Chapter 7

7ML5744-.....-

For applicable back up point level switch - see
point level measurement section

Selection and ordering data	Article No.	Article No.
SITRANS LR200 Radar level transmitter with horn Continuous, non-contact, 20 m (66 ft) range, for liquids and slurries. ↗ Click on the Article No. for the online configuration in the PIA Life Cycle Portal.	7ML5425-	7ML5425-
Antenna material (uses antenna adapter) 316L stainless steel with PTFE cone emitter 316L stainless steel with PTFE cone emitter and purge connection with 1/8" NPT inlet ¹⁾	0 1	0
Process connection (refer to Pressure/Temperature curves, page 4/259) Flanges (316L stainless steel) DN 50 PN 16 EN 1092-1 Type A flat faced ¹⁾ DN 80 PN 16 EN 1092-1 Type A flat faced DN 100 PN 16 EN 1092-1 Type A flat faced DN 150 PN 16 EN 1092-1 Type A flat faced DN 200 PN 16 EN 1092-1 Type A flat faced DN 80 PN 10/16 DIN EN 1092-1 Type B1 raised face ²⁾ DN 100 PN 10/16 DIN EN 1092-1 Type B1 raised face ³⁾ DN 150 PN 10/16 DIN EN 1092-1 Type B1 raised face ³⁾ DN 200 PN 16 DIN EN 1092-1 Type B1 raised face ³⁾ 2" ASME 150 lb, flat faced ¹⁾ 3" ASME 150 lb, flat faced 4" ASME 150 lb, flat faced 6" ASME 150 lb, flat faced 8" ASME 150 lb, flat faced DN 50 PN 40, flat faced ³⁾ DN 80 PN 40, flat faced ³⁾ DN 100 PN 40, flat faced ³⁾ DN 80 PN 25/40 DIN EN 1092-1 Type B1 raised face ³⁾ DN 100 PN 25/40 DIN EN 1092-1 Type B1 raised face ³⁾ DN 150 PN 25/40 DIN EN 1092-1 Type B1 raised face ³⁾ 2" ASME 300 lb, flat faced ¹⁾³⁾ 3" ASME 300 lb, flat faced ³⁾ 4" ASME 300 lb, flat faced ³⁾ JIS DN 50 10K ¹⁾ JIS DN 80 10K JIS DN 100 10K JIS DN 150 10K JIS DN 200 10K (Note: Flange bolting patterns and facings dimensionally correspond to the applicable ASME B16.5, or EN 1092-1, or JIS B 2220 standard.)	A A B A C A D A E A B F C F D F E F F B G B H B J B K B A C B C C C C G D G E G F D G D H D A E B E C E D E E E	Process seal/gasket FKM (-40 ... +200 °C)
		0
		2 3
		B C D E F G H J K L M N P Q R S
Enclosure/Cable inlet Aluminum, Epoxy painted 2 x 1/2" NPT 2 x M20 x 1.5		
Horn size/Waveguide options 80 mm (3 inch) horn ³⁾ 100 mm (4 inch) horn ⁴⁾ 150 mm (6 inch) horn 200 mm (8 inch) horn 100 mm (4 inch) horn with 100 mm (4 inch) waveguide extension ⁴⁾ 100 mm (4 inch) horn with 150 mm (6 inch) waveguide extension ⁴⁾ 100 mm (4 inch) horn with 200 mm (8 inch) waveguide extension ⁴⁾ 100 mm (4 inch) horn with 250 mm (10 inch) waveguide extension ⁴⁾ 150 mm (6 inch) horn with 100 mm (4 inch) waveguide extension 150 mm (6 inch) horn with 150 mm (6 inch) waveguide extension 150 mm (6 inch) horn with 200 mm (8 inch) waveguide extension 150 mm (6 inch) horn with 250 mm (10 inch) waveguide extension 200 mm (8 inch) horn with 100 mm (4 inch) waveguide extension 200 mm (8 inch) horn with 150 mm (6 inch) waveguide extension 200 mm (8 inch) horn with 200 mm (8 inch) waveguide extension 200 mm (8 inch) horn with 250 mm (10 inch) waveguide extension		
Communication/Output PROFIBUS PA 4 ... 20 mA, HART, start-up at < 3.6 mA	1 2	

Level measurement

Continuous level measurement Radar level transmitters

SITRANS LR200

Selection and ordering data

Article No.

Order code

SITRANS LR200 Radar level transmitter with horn

Continuous, non-contact, 20 m (66 ft) range, for liquids and slurries.

Approvals

Ordinary Locations/General Purpose (Non-Ex), CE, UKCA, RED, RCM

Ordinary Locations/General Purpose (Non-Ex), CSA, FM, IC, FCC

Intrinsically Safe, CSA Class I, II, Div. 1, Groups A, B, C, D, E, F, G, Industry Canada

Intrinsically Safe, FM Class I, II, Div. 1, Groups A, B, C, D, E, F, G, FCC

Intrinsically Safe;

ATEX II 1G Ex ia IIC T4 Ga;

UKEX II 1G Ex ia IIC T4 Ga;

IECEx Ex ia IIC T4 Ga;

INMETRO Ex ia IIC T4 Ga, IP67/IP68;

EAC Ex 0Ex ia IIC T4 Ga X;

CE, UKCA, RED, RCM, EAC

Non incendive, FM Class I, Div. 2,

Groups A, B, C, D, FCC⁴⁾

Increased Safety:

ATEX II 1/2G Ex eb mb ia IIC T4 Ga/Gb;

UKEX II 1/2G Ex eb mb ia IIC T4 Ga/Gb;

CE, UKCA, RED, RCM, EAC²⁾³⁾

Flameproof:

ATEX II 1/2G Ex db mb ia IIC T4 Ga/Gb;

UKEX II 1/2G Ex db mb ia IIC T4 Ga/Gb;

CE, UKCA, RED, RCM, EAC³⁾

Explosion Proof, CSA/FM Class I, II, III,

Groups A, B, C, D, E, F, G, Industry Canada, FCC⁵⁾⁷⁾

Pressure rating

Rating per Pressure/Temperature curves in manual
0.5 bar g (7.25 psi g) maximum

¹⁾ Available with pressure rating option 1 only.

²⁾ Available with Antenna Material options 0 and 1 only.

³⁾ For stillpipe applications only.

⁴⁾ Available with enclosure option 2 only.

⁵⁾ Available with enclosure option 3 only.

⁶⁾ Available with communication option 2 only.

⁷⁾ Available with Communication/Output option 2 only.

Article No.
7ML5425-
-
A
B
C
D
E
F
G
H
J
0
1

Further designs

Please add "-Z" to Article No. and specify Order code(s).

Stainless steel tag [69 x 50 mm (2.71 x 1.97 inch)]; Measuring-point number/identification (max. 27 characters); specify in plain text

Y15

Manufacturer's test certificate: M to DIN 55350, Part 18 and to ISO 9000

C11

Material inspection Certificate Type 3.1 per EN 10204

C12

Namur NE43 compliant, device preset to failsafe < 3.6 mA¹⁾

N07

Operating Instructions

All literature is available to download for free, in a range of languages, at

<http://www.siemens.com/processinstrumentation/documentation>

Accessories

Article No.

Handheld programmer, Intrinsically safe, EEx ia

7ML1930-1BK

HART modem/USB (for use with a PC and SIMATIC PDM)

7MF4997-1DB

One metallic cable gland M20 x 1.5, rated -40 ... +80 °C (-40 ... +176 °F), HART²⁾

7ML1930-1AP

One metallic cable gland M20 x 1.5, rated -40 ... +80 °C (-40 ... +176 °F), PROFIBUS PA³⁾

7ML1930-1AQ

One general purpose polymeric cable gland M20 x 1.5, rated -40 ... +80 °C (-40 ... +176 °F)

7ML1930-1AM

SITRANS RD100, loop powered display - see Chapter 7

7ML5741-.....-

SITRANS RD150, remote digital display for 4 ... 20 mA and HART devices - see Chapter 7

7ML5742-.....-..

SITRANS RD200, universal input display with Modbus conversion - see Chapter 7

7ML5740-.....-..

SITRANS RD300, dual line display with totalizer and linearization curve and Modbus conversion - see Chapter 7







7ML5744-.....-..

For applicable back up point level switch - see point level measurement section

¹⁾ Available with communication option 2 only.

²⁾ Product shipped with plastic cable gland, rated to -20 °C. If -40 °C rating required, then metallic cable gland is recommended.

³⁾ Available with enclosure option 2 only.

Selection and ordering data	Article No.	Article No.
SITRANS LR200 Specials		
SITRANS LR200 PROFIBUS PA aluminum enclosure kit with electronics and covers (7ML5422, 7ML5423, 7ML5424, 7ML5425), calibrated for use with standard rod antenna		Sun shield for SITRANS LR200 enclosure, stainless steel  A5E39142556
SITRANS LR200 aluminum enclosure with board stack, LUI display, 5.8 GHz, M20 cable inlet, approval option E, with PROFIBUS PA communication, no process connection.	A5E01483420	SITRANS LR200 horn antenna kits with mounting screws (no emitter supplied)  80 mm (3 inch) horn antenna kit PBD-25500K02A 100 mm (4 inch) horn antenna kit PBD-25500K03A 150 mm (6 inch) horn antenna kit PBD-25500K05A
SITRANS LR200 aluminum enclosure with board stack, LUI display, 5.8 GHz, M20 cable inlet, approval option A, with PROFIBUS PA communication, no process connection.	A5E01483440	SITRANS LR200 Extension Kits for Horn Antenna with mounting screw 100 mm (4 inch) extension kit for horn antenna PBD-25501K0100A 150 mm (6 inch) extension kit for horn antenna PBD-25501K0150A 200 mm (8 inch) extension kit for horn antenna PBD-25501K0200A 250 mm (10 inch) extension kit for horn antenna PBD-25501K0250A 500 mm (20 inch) extension kit for horn antenna PBD-25501K0500A 1 000 mm (40 inch) extension kit for horn antenna PBD-25501K1000A
SITRANS LR200 aluminum enclosure with board stack, LUI display, 6.3 GHz, M20 cable inlet, approval option C, with PROFIBUS PA communication, no process connection.	A5E01483456	SITRANS LR200 flanged rod antenna kit with 316L stainless steel flat faced flanges 
SITRANS LR200 aluminum enclosure with board stack, LUI display, 6.3 GHz, NPT cable inlet, approval option C, with PROFIBUS PA communication, no process connection.	A5E01483547	Flanged PTFE rod antenna kit, 2" ASME, 150 lb. See drawing 51003 on http://www.siemens.com/radar . ¹⁾⁴⁾ PBD-51003K020AAAA
SITRANS LR200 aluminum enclosure with board stack, LUI display, 5.8 GHz, NPT cable inlet, approval option E, with PROFIBUS PA communication, no process connection.	A5E01483559	Flanged PTFE rod antenna kit, DN 50 PN16. See drawing 51003 on http://www.siemens.com/radar . ¹⁾⁴⁾ PBD-51003K050AJAA
SITRANS LR200 HART aluminum enclosure kit with electronics and covers (7ML5422, 7ML5423, 7ML5424, 7ML5425), calibrated for use with standard rod antenna		Flanged PTFE rod antenna kit, JIS 10K DN 50. See drawing 51003 on http://www.siemens.com/radar . ¹⁾⁴⁾ PBD-51003K050AOAA
SITRANS LR200 aluminum enclosure with board stack, LUI display, 5.8 GHz, M20 cable inlet, approval option A, with HART communication start-up at < 3.6 mA, no process connection.	A5E02956419	SITRANS LR200 PTFE rod antenna kit with 316L stainless steel 1½" pipe thread process connection 
SITRANS LR200 aluminum enclosure with board stack, LUI display, 5.8 GHz, M20 cable inlet, approval option E, with HART communication start-up at < 3.6 mA, no process connection.	A5E02956420	PTFE rod antenna kit, R 1½" (BSPT), EN 10226 316L stainless steel process connection, FKM O-ring. See drawing 51004 on http://www.siemens.com/radar . ⁴⁾ PBD-51004K2AAA
SITRANS LR200 aluminum enclosure with board stack, LUI display, 5.8 GHz, M20 cable inlet, approval option G, with HART communication start-up at < 3.6 mA, no process connection.	A5E02956421	PTFE rod antenna kit, 1½" G 316L stainless steel process connection, FKM O-ring. See drawing 51004 on http://www.siemens.com/radar . ⁴⁾ PBD-51004K3AAA
SITRANS LR200 aluminum enclosure with board stack, LUI display, 5.8 GHz, M20 cable inlet, approval option H, with HART communication start-up at < 3.6 mA, no process connection.	A5E02956422	
SITRANS LR200 aluminum enclosure with board stack, LUI display, 5.8 GHz, NPT cable inlet, approval option A, with HART communication start-up at < 3.6 mA, no process connection.	A5E03617085	
SITRANS LR200 aluminum enclosure with board stack, LUI display, 6.3 GHz, NPT cable inlet, approval option B, with HART communication start-up at < 3.6 mA, no process connection.	A5E03617086	
SITRANS LR200 aluminum enclosure with board stack, LUI display, 5.8 GHz, NPT cable inlet, approval option C, with HART communication start-up at < 3.6 mA, no process connection.	A5E03617087	
SITRANS LR200 aluminum enclosure with board stack, LUI display, 6.3 GHz, NPT cable inlet, approval option E, with HART communication start-up at < 3.6 mA, no process connection.	A5E03617088	


Level measurement

Continuous level measurement
Radar level transmitters

SITRANS LR200

Selection and ordering data

SITRANS LR200 PTFE rod antenna kit with 316L stainless steel 2" pipe thread process connection



PTFE rod antenna kit, 2" NPT 316L stainless steel process connection, FKM O-ring. See drawing 51005 on <http://www.siemens.com/radar>.⁴⁾

PTFE rod antenna kit, R 2" (BSPT), EN 10226 316L stainless steel process connection, FKM O-ring. See drawing 51005 on <http://www.siemens.com/radar>.⁴⁾

PTFE rod antenna kit, 2" G 316L stainless steel process connection, FKM O-ring. See drawing 51005 on <http://www.siemens.com/radar>.⁴⁾

SITRANS LR200 PTFE rod antenna kit (100 mm shield) with 316L stainless steel 2" pipe thread process connection




PTFE rod antenna shielded kit, 2" NPT 316L stainless steel process connection, FKM O-ring, 100 mm 316L stainless steel shield. See drawing 51002 on <http://www.siemens.com/radar>.³⁾⁴⁾

PTFE rod antenna shielded kit, R 2" (BSPT), EN 10226 316L stainless steel process connection, FKM O-ring, 100 mm 316L stainless steel shield. See drawing 51002 on <http://www.siemens.com/radar>.³⁾⁴⁾

PTFE rod antenna shielded kit, 2" G 316L stainless steel process connection, FKM O-ring, 100 mm 316L stainless steel shield. See drawing 51002 on <http://www.siemens.com/radar>.³⁾⁴⁾

SITRANS LR200 horn antenna kit with 316L stainless steel flat faced flange, with PTFE emitter (without waveguide)



Horn antenna kit, 2" ASME 316L stainless steel flange 3" horn, PTFE emitter¹⁾⁴⁾

Horn antenna kit, 2" ASME 316L stainless steel flange 4" horn, PTFE emitter¹⁾²⁾

Horn antenna kit, 2" ASME 316L stainless steel flange 6" horn, PTFE emitter¹⁾²⁾

Horn antenna kit, 2" ASME 316L stainless steel flange 8" horn, PTFE emitter¹⁾²⁾

Horn antenna kit, DN 50 PN 16 316L stainless steel flange 80 mm horn, PTFE emitter¹⁾²⁾

Horn antenna kit, DN 50 PN 16 316L stainless steel flange 100 mm horn, PTFE emitter¹⁾²⁾

Horn antenna kit, DN 50 PN 16 316L stainless steel flange 150 mm horn, PTFE emitter¹⁾²⁾

Horn antenna kit, DN 50 PN 16 316L stainless steel flange 200 mm horn, PTFE emitter¹⁾²⁾

Article No.

PBD-51005K1AAA

PBD-51005K2AAA

PBD-51005K3AAA

PBD-51002K0100AAA

PBD-51002K0100BAA

PBD-51002K0100CAA

PBD-51006K020AAAA

PBD-51006K020AABA

PBD-51006K020ACAA

PBD-51006K020AADA

PBD-51006K050AJAA

PBD-51006K050AJBA

PBD-51006K050AJCA

PBD-51006K050AJDA

Article No.

SITRANS LR200 PTFE flanged rod antenna kit with 316L stainless steel shield and 316L stainless steel flat faced flange



PTFE shielded rod antenna kit, flanged, 3" ASME 150 lb 316L stainless steel flange, 100 mm 316L stainless steel shield.¹⁾⁴⁾

PTFE shielded rod antenna kit, flanged, DN 80 PN 16 316L stainless steel flange, 100 mm 316L stainless steel shield.¹⁾⁴⁾

PTFE shielded rod antenna kit, flanged, 3" ASME 150 lb 316L stainless steel flange, 150 mm 316L stainless steel shield.¹⁾⁴⁾

PTFE shielded rod antenna kit, flanged, DN 80 PN 16 316L stainless steel flange, 150 mm 316L stainless steel shield.¹⁾⁴⁾

PTFE shielded rod antenna kit, flanged, 3" ASME 150 lb 316L stainless steel flange, 200 mm 316L stainless steel shield.¹⁾⁴⁾

PTFE shielded rod antenna kit, flanged, DN 80 PN 16 316L stainless steel flange, 200 mm 316L stainless steel shield.¹⁾⁴⁾

PTFE shielded rod antenna kit, flanged, 3" ASME 150 lb 316L stainless steel flange, 250 mm 316L stainless steel shield.¹⁾⁴⁾

PTFE shielded rod antenna kit, flanged, DN 80 PN 16 316L stainless steel flange, 250 mm 316L stainless steel shield.¹⁾⁴⁾

PTFE paste

Kit, PTFE paste, Tube, 250 mL

Cable gland

One metallic cable gland M20 x 1.5, rated -40 ... +80 °C (-40 ... +176 °F), HART

One metallic cable gland M20 x 1.5, rated -40 ... +80 °C (-40 ... +176 °F), PROFIBUS PA

PBD-51014K0100AAA

PBD-51014K0100EJA

PBD-51014K0150AAA

PBD-51014K0150EJA

PBD-51014K0200AAA

PBD-51014K0200EJA

PBD-51014K0250AAA

PBD-51014K0250EJA

PBD-51036065


7ML1930-1AP

7ML1930-1AQ

- 1) Available in flange sizes including ASME, DIN and JIS. Please consult a local sales person for details.
- 2) Available with no pressure rating. Please consult a local sales person for details.
- 3) Available in other shield lengths. Please consult a local sales person for details.
- 4) Available with Pressure rating. Please consult a local sales person for details.

Customers interested in a custom designed device should consult a local sales person. For more information, please visit http://www.automation.siemens.com/aspa_app.

Characteristic curves






SITRANS LR200 ambient/process flange surface temperature curve

Level measurement

Continuous level measurement
Radar level transmitters


SITRANS LR200

Characteristic curves (continued)



SITRANS LR200 process pressure/temperature derating curves

Dimensional drawings




SITRANS LR200, dimensions in mm (inch)

Level measurement

Continuous level measurement
Radar level transmitters



SITRANS LR200

Circuit diagrams




El suministro puede incluir el pasacables, depende de la homologación seleccionada.

Conectar los cables con los terminales como se indica: polaridad indicada en los terminales.

Blindaje para HART y PROFIBUS PA: sólo para versiones de seguridad intrínseca.

Programador portátil



Referencia:
7ML1930-1BK

Notas:

1. Los bornes (DC) deberían recibir el suministro eléctrico de una fuente de alimentación SELV en conformidad con la norma IEC 61010-1 Anexo H.
2. Aislar todos los cableados tomando en cuenta las tensiones utilizadas.
3. Utilizar cable par trenzado apantallado (grosor 14 ... 22 AWG).
4. Para la instalación eléctrica deben observarse las normas y disposiciones pertinentes. Pueden ser necesarios cables y conductos separados.

SITRANS LR200 connections