Pressure transmitters

Single-range transmitters / SITRANS P200

Overview



The SITRANS P200 pressure transmitter measures the gauge and absolute pressure of liquids, gases and vapors.

- With ceramic measuring cell
- Gauge and absolute measuring ranges 1 to 60 bar (15 to 1000 psi)
- For general applications

Benefits

- High measurement accuracy
- Rugged stainless steel enclosure
- High overload withstand capability
- For corrosive and non-corrosive media
- For measuring the pressure of liquids, gases and vapors
- Compact design

Application

The SITRANS P200 pressure transmitter for gauge and absolute pressure is used in the following industrial areas:

- Mechanical engineering
- Shipbuilding
- Power engineering
- Chemical industry
- Water supply

Design

Device structure without explosion protection

The pressure transmitter consists of a piezoresistive measuring cell with a diaphragm, installed in a stainless steel enclosure. It can be connected electrically with a device plug to EN 175301-803-A (IP65), an M12 device plug (IP67), a cable (IP67) or a Quickon cable quick screw connection (IP67). The output signal is between 4 and 20 mA or 0 and 10 V


Device structure with explosion protection

The pressure transmitter consists of a piezoresistive measuring cell with a diaphragm, installed in a stainless steel enclosure. It can be connected electrically with a device plug fulfilling EN 175301-803-A (IP65) or an M12 device plug (IP67). The output signal is between 4 and 20 mA.

Function

The pressure transmitter measures the gauge and absolute pressure of liquids, gases and vapors.

Mode of operation



SITRANS P200 pressure transmitters (7MF1565-...), functional diagram

The ceramic measuring cell has a thick-film resistance bridge, to which the operating pressure p is transmitted through a ceramic diaphragm.

The voltage output from the measuring cell is converted by an amplifier into an output current of 4 to 20 mA or an output voltage of 0 to 10 V DC.

The output current and voltage are linearly proportional to the input pressure.

Pressure transmitters

Single-range transmitters / SITRANS P200

Selection and ordering data

								Article No. 7MF1565-					Order code				
ITRANS P2		transmit	tter, for press	ure and abs	olute pressu	re for gene	ral										
								•	•	• •	•	- • •	• •		• (•	
arts: Ceramic	eristic curve devia and stainless stee n-wetted parts: Sta	l + gasket m	material of wetted aterial														
			ration in the PIA L	ife Cycle Portal.				П								Т	
Measuring ran	nge	Minimum (overload limit	Maximum o	verload limit	Burst pressur	·e										
or gauge pres	ssure																
1 bar	(0 14.5 psi)	-1 bar	(-14.5 psi)	2.5 bar	(36.26 psi)	> 2.5 bar	(> 36.3 psi)	3	В	Α							
1.6 bar	(0 23.2 psi)	-1 bar	(-14.5 psi)	4 bar	(58.02 psi)	> 4 bar	(> 58.0 psi)	3	В	В							
2.5 bar	(0 36.3 psi)	-1 bar	(-14.5 psi)	6.25 bar	(90.65 psi)	> 6.25 bar	(> 90.7 psi)	3	В	D							
4 bar	(0 58.0 psi)	-1 bar	(-14.5 psi)	10 bar	(145 psi)	> 10 bar	(> 145 psi)	3	В	Е							
6 bar	(0 87.0 psi)	-1 bar	(-14.5 psi)	15 bar	(217 psi)	> 15 bar	(> 217 psi)	3	В	G							
10 bar	(0 145 psi)	-1 bar	(-14.5 psi)	25 bar	(362 psi)	> 25 bar	(> 362 psi)	3	C	Α							
16 bar	(0 232 psi)	-1 bar	(-14.5 psi)	40 bar	(580 psi)	> 40 bar	(> 580 psi)	3	C	В							
25 bar	(0 363 psi)	-1 bar	(-14.5 psi)	62.5 bar	(906 psi)	> 62.5 bar	(> 906 psi)	3	C	D							
40 bar	(0 580 psi)	-1 bar	(-14.5 psi)	100 bar	(1450 psi)	> 100 bar	(> 1450 psi)	3	C	E							
60 bar	(0 870 psi)	-1 bar	(-14.5 psi)	150 bar	(2175 psi)	> 150 bar	(> 2175 psi)	3	C	G							
ther version; /	Add order code a	nd plain text:	: Measuring range:	to bar (psi)				9	Α	Α					н :	1	
or absolute p	ressure																
0.6 bar a	(0 8.7 psi a)	0 bar a	(0 psi a)	2.5 bar a	(36.26 psi a)	> 2.5 bar a	(> 36.3 psi a)	5	Α	G							
1 bar a	(0 14.5 psi a)	0 bar a	(0 psi a)	2.5 bar a	(36.26 psi a)	> 2.5 bar a	(> 36.3 psi a)	5	В	Α							
1.6 bar a	(0 23.2 psi a)	0 bar a	(0 psi a)	4 bar a	(58.02 psi a)	> 4 bar a	(> 58.0 psi a)	5	В	В							
2.5 bar a	(0 36.3 psi a)	0 bar a	(0 psi a)	6.25 bar a	(90.65 psi a)	> 6.25 bar a	(> 90.7 psi a)	5	В	D							
4 bar a	(0 58.0 psi a)	0 bar a	(0 psi a)	10 bar a	(145 psi a)	> 10 bar a	(> 145 psi a)	5	В	Е							
6 bar a	(0 87.0 psi a)	0 bar a	(0 psi a)	15 bar a	(217 psi a)	> 15 bar a	(> 217 psi a)	5	В	G							
10 bar a	(0 145 psi)	0 bar a	(0 psi a)	25 bar a	(362 psi a)	> 25 bar a	(> 362 psi a)	5	С	Α							
16 bar a	(0 232 psi)	0 bar a	(0 psi a)	40 bar a	(580 psi a)	> 40 bar a	(> 580 psi a)	5	С	В							
ther version; /	Add order code a	nd plain text:	: Measuring range:	to mbar a (psi a)			9	Α	Α					н :	2	
leasuring ran	nges for gauge p	ressure															
	0 15 psi		-14.5 psi		35 psi		> 35 psi	4	В	В							
	3 15 psi		-14.5 psi		35 psi		> 35 psi	4	В	С							
	0 20 psi		-14.5 psi		50 psi		> 50 psi	4	В	D							
	0 30 psi		-14.5 psi		80 psi		> 80 psi	4	В	Е							
	0 60 psi		-14.5 psi		140 psi		> 140 psi	4	В	F							
	0 100 psi		-14.5 psi		200 psi		> 200 psi	4	В	G							
	0 150 psi		-14.5 psi		350 psi		> 350 psi	4	С	Α							
	0 200 psi		-14.5 psi		550 psi		> 550 psi	4	С								
	0 300 psi		-14.5 psi		800 psi		> 800 psi	4	С								
	0 500 psi		-14.5 psi		1 400 psi		> 1400 psi	4	С								
	0 750 psi		-14.5 psi		2 000 psi		> 2 000 psi	4	C								
	0 1 000 psi		-14.5 psi		2 000 psi		> 2 000 psi	4	C								
ther version:		nd plain text	: Measuring range:	to nsi	2 000 ps.		, 2 000 ps.	9	Α						Н	1	
	iges for absolute		. measaring ranger	to psi						-				_		÷	
	0 10 psi a	pressure	0 psi a		35 psi a		> 35 psi a	6	Α	G							
	0 15 psi a		0 psi a		35 psi a		> 35 psi a	6	В								
	0 19 psi a		0 psi a		50 psi a		> 50 psi a	6	В								
	0 30 psi a		0 psi a		80 psi a		> 80 psi a	6		D							
	0 60 psi a		0 psi a		140 psi a		> 140 psi a	6		E							
	0 100 psi a		0 psi a 0 psi a		200 psi a		> 200 psi a	6	В								
	0 100 psi a		0 psi a 0 psi a		350 psi a		> 200 psi a > 350 psi a	6	С								
	0 150 psi a		0 psi a 0 psi a		550 psi a			6	C								
			0 psi a 0 psi a				> 550 psi a	6	C								
thor version	0 300 psi a	ad plain to t	U psi a : Measuring range:	to poi o	800 psi a		> 800 psi a								u .	_	
	Aud order code al	iu piain text:	. ivieasuring range:	to psi a				9	Α	А				-	Н :	_	
Output signal 4 20 mA; 2-v	wire system; auxil	iary power 7	33 V DC (10 3	0 V DC for ATEX	devices)					C)						

Pressure transmitters

Single-range transmitters / SITRANS P200

Selection and ordering data (continued)

	Article No.								Order		
SITRANS P200 pressure transmitter, for pressure and absolute pressure for general	7N		CO	ue							
applications											
	•	•	• •	•	- •	•	• •		•	•	
0 5 V; 3-wire system; auxiliary power 7 33 V DC				0							
Ratiometric 10 90%; 3-wire system; auxiliary power 5 V DC ± 10%			3	0							
Explosion protection (only 4 20 mA)											
None				0							
With explosion protection Ex ia IIC T4				1							
Electrical connection											
Plug according to EN 175301-803-A, stuffing box thread M16 (with coupling)					1						
M12 device plug according to IEC 61076-2-101					2						
Connection via permanently installed cable, 2 m (6.6 ft); not for "Intrinsic safety" type of protection				0	3						
Quick-screw cable gland Quickon PG9; not for "Intrinsic safety" type of protection				0	4						
Plug according to EN 175301-803-A, stuffing box thread 1/2"-14 NPT (with coupling)					5						
Plug according to EN 175301-803-A, stuffing box thread PG11 (with coupling)					6						
Permanently installed cable, length 5 m (16.4 ft)				0	7						
Special design					9				N	1 Y	
Process connection											
G½" male according to EN 837-1 (½" BSP male): Standard for metric pressure ranges mbar, bar						Α					
G½" male and G1/8" female						В					
G¼" male according to EN 837-1 (¼" BSP male)						C					
7/16"-20 UNF male						D					
$\mbox{\ensuremath{\%}}$ "-18 NPT male: Standard for pressure ranges in $\mbox{\ensuremath{H}}_2\mbox{O}$ and psi						E					
1/4"-18 NPT female						F					
½"-14 NPT male						G					
½"-14 NPT female						Н					
7/16"-20 UNF female						J					
M20×1.5 male						Р					
G¼" according to EN ISO 1179-2 (formerly DIN 3852 form E)						Q					
G½" according to EN ISO 1179-2 (formerly DIN 3852 form E)						R					
Special design						Z			Р	1 Y	
Gasket material between sensor and enclosure											
Viton (FPM, standard)							Α				
Neoprene (CR)							В				
Perbunan (NBR)							C				
EPDM							D				
Special design							Z		Q	1 Y	
Version											
Standard version							1				

Options	Order code
Add "-Z" to article number and specify order code.	
Quality inspection certificate (5-point characteristic curve test) according to IEC 62828-2	C11
Oxygen version, free of oil and degreased, max. operating pressure 60 bar (870.2 psi), max. medium temperature +85 $^{\circ}$ C (185 $^{\circ}$ F)	E10
<u>Notice</u>	
Only with Viton gasket material between sensor and enclosure, and not with explosion protection version!	

Pressure measurement Pressure transmitters

Single-range transmitters / SITRANS P200

Technical specifications

Area of application	
Gauge and absolute pressure measurement	Liquids, gases and vapors
Mode of operation	Diaza resistive measuring call (coromic
Measuring principle	Piezo-resistive measuring cell (ceramic diaphragm)
Measured variable	Gauge and absolute pressure
Input	
Measuring range	
Gauge pressure	
- Metric	1 60 bar (15 870 psi)
- US measuring range	15 1000 psi
Absolute pressure	
- Metric	0.6 16 bar a (10 232 psi a)
- US measuring range	10 300 psi a
Output	
Current signal	4 20 mA
• Load	(U _B - 10 V)/0.02 A
Auxiliary power U _B	7 33 V DC (10 30 V for Ex)
Voltage signal	0 10 V DC
• Load	≥ 10 kΩ
Auxiliary power U _B	12 33 V DC
Current consumption	< 7 mA at 10 kΩ
Radiometric output	10 90%
• Load	≥ 10 kΩ
Auxiliary power U _B	DC 5 V ± 10%
Current consumption	< 7 mA at 10 Ω
Characteristic curve	
Measuring accuracy	Linear rising
Measurement deviation at limit setting including hysteresis and reproducibility	Typical: 0.25% of measuring span Maximum: 0.5% of measuring span
Step response time T ₉₉	< 5 ms
Long-term stability	
Lower range value and measuring span	0.25% of measuring span/year
Effect of ambient temperature	
Lower range value and measuring span	0.25%/10 K of measuring span
Influence of power supply	0.005%/V
Operating conditions	
Process temperature with gasket made of:	
• FPM (standard)	-15 +125 °C (5 257 °F)
Neoprene	-35 +100 °C (-31 +212 °F)
Perbunan	-20 +100 °C (-4 +212 °F)
• EPDM	-40 +125 °C (-40 +257 °F), usable for
Ambient temperature	-25 +85 °C (-13 +185 °F)
Storage temperature	-50 +100 °C (-58 +212 °F)
Degree of protection according to IEC 60529	IP65 with plug according to EN 175301-803-A
	IP67 with M12 device plug
	• IP67 with cable
	IP67 with cable quick screw connection
Electromagnetic compatibility	• According to IEC 61326-1/-2/-3
	 According to NAMUR NE21 for ATEX devices only, and with a max. measure ment error of ≤ 1%
Structural design	
Weight	Approx. 0.090 kg (0.198 lbs)
	See dimension drawings

Technical specifications (continued)


SITRANS P200 for gauge and absolute pressure Electrical connections • Plug according to EN 175301-803-A Form								
 Plug according to EN 175301-803-A Form A with cable entry M16x1.5 or ½-14 NPT or Pg 11 								
Device plug M12								
• 2 or 3-wire (0.5 mm²) cable (Ø ± 5.4 mr								
Quickon cable quick screw connection								
Al ₂ O ₃ - 96%								
Stainless steel, mat. no. 1.4404 (SST 316 L)								
• FPM (standard)								
Neoprene								
Perbunan								
• EPDM								
Stainless steel, mat. no. 1.4404 (SST 316 L)								
Plastic								
PVC								
For gases of fluid group 1 and liquids of fluid group 1; complies with requirements of article 4, paragraph 3 (sound engineering practice)								
12/20010								
GL19740 11 HH00								
ABS_11_HG 789392_PDA								
BV 271007A0 BV								
A 12553								
ACS 15 ACC NY 360								
№ TC RU C-DE.ГБ05.В.00732 ОС НАНИО «ЦСВЭ»								
UL 20110217 - E34453								
IEC UL DK 21845								
Ex II 1/2 G Ex ia IIC T4 Ga/Gb Ex II 1/2 D Ex ia IIIC T125 °C Da/Db								
SEV 10 ATEX 0146								
$U_i \le DC \ 30 \ V; \ I_i \le 100 \ mA; \ P_i \le 0.75 \ W$								

¹⁾ For variants with output signal 0 ... 5 V and radiometric output available soon

Pressure transmitters


Single-range transmitters / SITRANS P200

Dimensional drawings



SITRANS P200, electrical connections, dimensions in mm (inch)

Dimensional drawings (continued)




SITRANS P200, process connections, dimensions in mm (inch)


Pressure transmitters

Single-range transmitters / SITRANS P200


Circuit diagrams




Connection with current output and plug according to EN 175301




Connection with current output and M12x1 device plug



Connection with current output and cable




Connection with current output and Quickon cable quick screw connection




Connection with voltage output, ratiometric output and plug according to EN 175301


Circuit diagrams (continued)



Connection with voltage output, ratiometric output and M12x1 device pluq




Connection with voltage output, ratiometric output and cable




Connection with voltage output, ratiometric output and Quickon fast cable termination

Device design with explosion protection: 4 to 20 mA

The grounding connection is conductively bonded to the transmitter enclosure.



Connection with current output and plug according to EN 175301 (Ex)



Connection with current output and M12x1 (Ex) device plug

Pressure transmitters

Single-range transmitters / SITRANS P210

Overview



The SITRANS P210 pressure transmitter measures the gauge pressure of liquids, gases and vapors.

- Stainless steel measuring cell
- Measuring ranges 100 to 600 mbar (1.45 to 8.7 psi) relative
- For low-pressure applications

Benefits

- High measurement accuracy
- Rugged stainless steel enclosure
- High overload withstand capability
- For corrosive and non-corrosive media
- For measuring the pressure of liquids, gases and vapors
- Compact design

Application

The SITRANS P210 pressure transmitter for gauge pressure is used in the following industrial areas:

- · Mechanical engineering
- Shipbuilding
- Energy development
- Chemical industry
- Water supply

Design

Device structure without explosion protection

The pressure transmitter consists of a piezoresistive measuring cell with a diaphragm, installed in a stainless steel enclosure. It can be connected electrically with a device plug to EN 175301-803-A (IP65), an M12 device plug (IP67), a cable (IP67) or a Quickon cable quick screw connection (IP67). The output signal is between 4 and 20 mA or 0 and 10 V


Device structure with explosion protection

The pressure transmitter consists of a piezoresistive measuring cell with a diaphragm, installed in a stainless steel enclosure. It can be connected electrically with a device plug fulfilling EN 175301-803-A (IP65) or an M12 device plug (IP67). The output signal is between 4 and 20 mA.

Function

The pressure transmitter measures the gauge pressure of liquids and gases as well as the level of liquids.

Mode of operation



SITRANS P210 pressure transmitter (7MF1566-...), functional diagram

The stainless steel measuring cell with silicone oil filling has a thinfilm resistance bridge to which the operating pressure p is transmitted through a stainless steel diaphragm.

The voltage output from the measuring cell is converted by an amplifier into an output current of 4 to 20 mA or an output voltage of 0 to 10 V DC.

The output current and voltage are linearly proportional to the input pressure.

Pressure transmitters

Single-range transmitters / SITRANS P210

Selection and ordering data

									Article No.								er	
SITRANS P	210 pressur	re transmitte	r for gauge	pressure, fo	or low-pres	sure applic	ations	7MF1566-							code			
Material of we		less steel + gasket	t material					•	•	•	•	• -	•	• (•	•	•	
	n-wetted parts: !	online configurat	ion in the PIA I	ife Cycle Portal					-	-	_	-					-	-
Measuring rai		Minimum ove		Maximum ov	erload limit	Burst pres	SIIFA			_		-					-	-
For gauge pre		William GVC	inoud illinit	Widainiani ov	CHOUGHIIIIC	Buist pies	Juic	_		_								+
0100 mbar	(1.45 psi)	-400 mbar	(-5.8 psi)	400 mbar	(5.8 psi)	1 bar	(14.5 psi)	3	Α	Α								
0160 mbar	(2.32 psi)	-400 mbar	(-5.8 psi)	400 mbar	(5.8 psi)	1 bar	(14.5 psi)	3	Α	В								
0250 mbar	(3.63 psi)	-800 mbar	(-11.6 psi)	1 000 mbar	(14.5 psi)	2 bar	(29.0 psi)	3		С								
0400 mbar	(5.8 psi)	-800 mbar	(-11.6 psi)	1 000 mbar	(14.5 psi)	2 bar	(29.0 psi)	3	Α	D								
0600 mbar	(8.7 psi)	-1 000 mbar	(-14.5 psi)	2 000 mbar	(29.0 psi)	3 bar	(43.5 psi)	3	Α	G								
Other version;	Add order code ge: to mba	and plain text:	, ,,,		, ,		,,	9	Α							Н	1	,
Output signal																		
		xiliary power 7	33 V DC (10 3	0 V DC for ATEX	devices)						0							
0 10 V; 3-wi	re system; auxil	iary power 12 3	33 V DC								1	0						
0 5 V; 3-wire	e system; auxilia	ary power 7 33	V DC								2	0						
Ratiometric 10	90%; 3-wire	system; auxiliary	power 5 V DC ±	10%							3	0						
Explosion pro	tection (only 4	20 mA)																
None												0						
With explosion	protection Ex ia	a IIC T4										1						
Electrical con	nection																	
Plug according to EN 175301-803-A, stuffing box thread M16 (with coupling)													1					
M12 device plu	ug according to	IEC 61076-2-101											2					
Connection via permanently installed cable, 2 m (6.6 ft); not for "Intrinsic safety" type of protection												0	3					
Quick-screw ca	able gland Quick	on PG9; not for "I	ntrinsic safety" t	ype of protection								0	4					
Plug according	to EN 175301-	803-A, stuffing bo	x thread 1/2"-14	NPT (with coupli	ng)								5					
Plug according	to EN 175301-	803-A, stuffing bo	x thread PG11 (with coupling)									6					
Permanently in	nstalled cable, le	ngth 5 m (16.4 ft)									0	7					
Special design													9			N	1	١
Process conne	ection																	
G½" male acco	rding to EN 837	'-1 (½" BSP male):	Standard for me	etric pressure rang	ges mbar, bar									Α				
G½" male and														В				
G¼" male acco	rding to EN 837	'-1 (¼" BSP male)												C				
7/16"-20 UNF r	male													D				
1/4"-18 NPT mal	le: Standard for	pressure ranges ir	nH ₂ O and psi											E				
1/4"-18 NPT fem														F				
½"-14 NPT mal														G				
½"-14 NPT fem														Н				
7/16"-20 UNF f														J				
M20×1.5 male														Р				
G¼" according to EN ISO 1179-2 (formerly DIN 3852 form E)														Q				
G½" according to EN ISO 1179-2 (formerly DIN 3852 form E)														R			4	
Special design														Z		Р	1	_
		nsor and enclosu	re															
Viton (FPM, standard)																		
Neoprene (CR) Perbunan (NBR)																		
Perbunan (NBF	()																	
EPDM																0	1	
Special design														- 2		Q	1	_ Y
Version																		
Standard version	on														1			

Options	Order code
Add "-Z" to article number and specify order code.	
Quality inspection certificate (5-point characteristic curve test) according to IEC 62828-2	C11

Pressure transmitters

Single-range transmitters / SITRANS P210

Technical specifications

CITE AND DOZO (
SITRANS P210 for gauge pressure								
Area of application	l							
Gauge pressure measurement	Liquids, gases and vapors							
Mode of operation	Biological Control of the Control of							
Measuring principle Measured variable	Piezoresistive measuring cell (stainless steel diaphragm) Gauge pressure							
Input	dauge pressure							
Measuring range								
Gauge pressure	100 600 mbar (1.45 8.7 psi)							
Output								
Current signal	4 20 mA							
• Load	(U _B - 10 V)/0.02 A							
Auxiliary power U _B	7 33 V DC (10 30 V for Ex)							
Voltage signal • Load	0 10 V DC ≥ 10 kΩ							
Auxiliary power U _B	12 33 V DC							
Current consumption	< 7 mA at 10 kΩ							
Radiometric output	10 90%							
• Load	≥ 10 kΩ							
Auxiliary power U _B	DC 5 V ± 10%							
Current consumption	$<$ 7 mA at 10 k Ω							
Characteristic curve	Linear rising							
Measuring accuracy								
Measurement deviation at limit setting including hysteresis and reproducibility	Typical: 0.25% of measuring span Maximum: 0.5% of measuring span							
Step response time T ₉₉	< 5 ms							
Long-term stability								
Lower range value and measuring span	0.25% of measuring span/year							
Effect of ambient temperature								
Lower range value and measuring span	• 0.25%/10 K of measuring span							
	0.5%/10 K of measuring span for a measuring range 100 400 mbar (40 240 inH ₂ O)							
Influence of power supply	0.005%/V							
Operating conditions								
Process temperature with gasket made of:								
• FPM (standard)	-15 +125 °C (5 257 °F)							
Neoprene	-35 +100 °C (-31 +212 °F)							
Perbunan	-20 +100 °C (-4 +212 °F)							
• EPDM	-40 +125 °C (-40 +257 °F), usable for drinking water							
Ambient temperature	-25 +85 °C (-13 +185 °F)							
Storage temperature	-50 +100 °C (-58 +212 °F)							
Type of protection according to IEC 60529	IP65 with plug according to EN 175301-803-A							
	IP67 with M12 device plug							
	IP67 with cable							
	IP67 with cable quick screw connection							
Electromagnetic compatibility	• According to IEC 61326-1/-2/-3							
	According to NAMUR NE21 for ATEX devices only, and with a max. measure- ment error of ≤ 1%							
Mounting position	Vertical, facing up							
Structural design								
Weight	Approx. 0.090 kg (0.198 lbs)							
Process connections	See dimension drawings							

Technical specifications (continued)


SITRANS P210 for gauge pressu	re						
Electrical connections	Plug according to EN 175301-803-A Form A with cable entry M16x1.5 or ½-14 NPT or Pg 11						
	Device plug M12						
	• 2 or 3-wire (0.5 mm²) cable (Ø ± 5.4 mm)						
	Quickon cable quick screw connection						
Material of wetted parts							
Measuring cell	Stainless steel, mat. no. 1.4435						
Process connection	Stainless steel, mat. no. 1.4404 (SST 316 L)						
• Gasket	• FPM (standard)						
	Neoprene						
	Perbunan						
	• EPDM						
Material of non-wetted parts							
• Enclosure	Stainless steel, mat. no. 1.4404 (SST 316 L)						
Connector housing	Plastic						
• Cable	PVC						
Certificates and approvals							
Classification according to pressure equipment directive (PED 2014/68/EU)	For gases of fluid group 1 and liquids of fluid group 1; meets requirements as per article 4, paragraph 3 (sound engineering practice)						
Lloyd's Register of Shipping (LR) ¹⁾	12/20010						
Germanischer Lloyd (GL) ¹⁾	GL19740 11 HH00						
American Bureau of Shipping (ABS) ¹⁾	ABS_11_HG 789392_PDA						
Bureau Veritas (BV)1)	BV 271007A0 BV						
Det Norske Veritas (DNV) ¹⁾	A 12553						
Drinking water approval (ACS) ¹⁾	ACS 15 ACC NY 360						
EAC ¹⁾	№ TC RU C-DE.ГБ05.В.00732 ОС НАНИО «ЦСВЭ»						
Underwriters Laboratories (UL)1)							
For the USA and Canada	UL 20110217 - E34453						
Worldwide	IEC UL DK 21845						
Explosion protection							
Intrinsic safety "i" (only with current output)	Ex II 1/2 G Ex ia IIC T4 Ga/Gb Ex II 1/2 D Ex ia IIIC T125 °C Da/Db						
EC type-examination certificate	SEV 10 ATEX 0146						
Connection to certified intrinsically safe ohmic circuits with maximum values	$U_i \le DC 30 \text{ V}; I_i \le 100 \text{ mA}; P_i \le 0.75 \text{ W}$						
Effective internal inductance and capacity for versions with plugs according to EN 175301-803-A and M12	L _i = 0 nH; C _i = 0 nF						

1) For variants with output signal 0 ... 5 V and radiometric output available soon.

Pressure transmitters


Single-range transmitters / SITRANS P210

Dimensional drawings



SITRANS P210, electrical connections, dimensions in mm (inch)

Dimensional drawings (continued)




SITRANS P210, process connections, dimensions in mm (inch)


Pressure transmitters

Single-range transmitters / SITRANS P210


Circuit diagrams




Connection with current output and plug according to EN 175301




Connection with current output and M12x1 device plug



Connection with current output and cable




Connection with current output and Quickon cable quick screw connection




Connection with voltage output, ratiometric output and plug according to EN 175301


Circuit diagrams (continued)



Connection with voltage output, ratiometric output and M12x1 device pluq




Connection with voltage output, ratiometric output and cable




Connection with voltage output, ratiometric output and Quickon fast cable termination

Device design with explosion protection: 4 to 20 mA

The grounding connection is conductively bonded to the transmitter enclosure.



Connection with current output and plug according to EN 175301 (Ex)



Connection with current output and M12x1 (Ex) device plug

Pressure transmitters

Single-range transmitters / SITRANS P220

Overview



The SITRANS P220 pressure transmitter measures the gauge pressure of liquids, gases and vapors.

- Stainless steel measuring cell, fully welded
- Measuring ranges 2.5 to 1 000 bar (36.3 to 14 500 psi) relative
- For high-pressure applications and refrigeration technology

Benefits

- High measurement accuracy
- Rugged stainless steel enclosure
- High overload withstand capability
- For corrosive and non-corrosive media
- For measuring the pressure of liquids, gases and vapors
- Compact design
- Gasket-less

Application

The SITRANS P220 pressure transmitter for gauge pressure is used in the following industrial areas:

- Mechanical engineering
- Shipbuilding
- Energy development
- Chemical industry
- Water supply

Design

Device structure without explosion protection

The pressure transmitter consists of a piezoresistive measuring cell with a diaphragm, installed in a stainless steel enclosure. It can be connected electrically with a device plug to EN 175301-803-A (IP65), an M12 device plug (IP67), a cable (IP67) or a Quickon cable quick screw connection (IP67). The output signal is between 4 and 20 mA or 0 and 10 V


Device structure with explosion protection

The pressure transmitter consists of a piezoresistive measuring cell with a diaphragm, installed in a stainless steel enclosure. It can be connected electrically with a device plug fulfilling EN 175301-803-A (IP65) or an M12 device plug (IP67). The output signal is between 4 and 20 mA.

Function

The pressure transmitter measures the gauge pressure of liquids and gases as well as the level of liquids.

Mode of operation



SITRANS P220 pressure transmitters (7MF1567-...), functional diagram

The stainless steel measuring cell has a thick-film resistance bridge to which the operating pressure p is transmitted through a stainless steel diaphragm.

The voltage output from the measuring cell is converted by an amplifier into an output current of 4 to 20 mA or an output voltage of 0 to 10 V DC.

The output current and voltage are linearly proportional to the input pressure.

Pressure transmitters

Single-range transmitters / SITRANS P220

Selection and ordering data

								Aı	rtic	le N	lo.					Order code		
			tter for gauge	pressure, f	or high-pres	sure and co	old	71	/F15	67-					C	oue		
pplicatio	ns, fully-wel	ded versi	on						•	•	•	• -	•	• A	•	•	•	
Material of we	deviation typ. 0.2 etted parts: Stainle n-wetted parts: St	ess steel						Г										
			ration in the PIA L	fe Cycle Portal.				-		_								
Measuring ra			overload limit		verload limit	Burst pressu	ıre											
For gauge pre																		
0 2.5 bar	(0 36.3 psi)	-1 bar	(-14.5 psi)	6.25 bar	(90.7 psi)	25 bar	(363 psi)	3	В	D								
0 4 bar	(0 58 psi)	-1 bar	(-14.5 psi)	10 bar	(145 psi)	40 bar	(580 psi)	3	В	Е								
0 6 bar	(0 87 psi)	-1 bar	(-14.5 psi)	15 bar	(217 psi)	60 bar	(870 psi)	3		G								
0 10 bar	(0 145 psi)	-1 bar	(-14.5 psi)	25 bar	(362 psi)	60 bar	(870 psi)	3	С	Α								
0 16 bar	(0 232 psi)	-1 bar	(-14.5 psi)	40 bar	(580 psi)	96 bar	(1 392 psi)	3	C	В								
0 25 bar	(0 363 psi)	-1 bar	(-14.5 psi)	62.5 bar	(906 psi)	150 bar	(2 176 psi)	3		D								
0 40 bar	(0 580 psi)	-1 bar	(-14.5 psi)	100 bar	(1 450 psi)	240 bar	(3 481 psi)	3	C									
0 60 bar				150 bar		360 bar		3		G								
0 100 bar	(0 870 psi)	-1 bar	(-14.5 psi)	250 bar	(2 175 psi)	600 bar	(5 221 psi) (8 702 psi)	3		A								
	(0 1450 psi)		(-14.5 psi)		(3 625 psi) (5 901 psi)		(8 702 psi)											
0 160 bar	(0 2320 psi)		(-14.5 psi)	400 bar	(5 801 psi)	960 bar	(13 924 psi)	3	D	В								
0 250 bar	(0 3625 psi)		(-14.5 psi)	625 bar	(9 064 psi)	1 500 bar	(21 756 psi)	3		D								
0 400 bar	(0 5801 psi)		(-14.5 psi)	1 000 bar	(14 503 psi)	2 400 bar	(34 809 psi)			E								
) 600 bar	(0 8702 psi)		(-14.5 psi)	1 500 bar	(21 755 psi)	3 600 bar	(52 200 psi)			G								
0 1000 bar			(-14.5 psi)	1 500 bar	(21 755 psi)	5 000 bar	(72 520 psi)		E									
			: Measuring range:	to bar (psi)				9	Α	Α	_	-				Н	1	
Measuring ra	nges for gauge p	ressure																
	0 30 psi		-14.5 psi		75 psi		360 psi	4	В		1)							
	0 60 psi		-14.5 psi		150 psi		580 psi	4	В	F	1)							
	0 100 psi		-14.5 psi		250 psi		580 psi	4	В	G	1)							
	0 150 psi		-14.5 psi		375 psi		870 psi	4	C	Α	1)							
	0 200 psi		-14.5 psi		500 psi		1 390 psi	4	C	В	1)							
	0 300 psi		-14.5 psi		750 psi		2 170 psi	4	C	D	1)							
	0 500 psi		-14.5 psi		1 250 psi		3 481 psi	4	C	Ε	1)							
	0 750 psi		-14.5 psi		1 875 psi		5 220 psi	4	C	F	1)							
	0 1 000 psi		-14.5 psi		2 500 psi		5 220 psi	4	C	G	1)							
	0 1 500 psi		-14.5 psi		3 750 psi		8 700 psi	4	D	Α	1)							
	0 2 000 psi		-14.5 psi		5 000 psi		13 920 psi	4	D	В	1)							
	0 3 000 psi		-14.5 psi		7 500 psi		21 750 psi	4	D	D	1)							
	0 5 000 psi		-14.5 psi		12 500 psi		34 800 psi	4	D	E	1)							
	0 6 000 psi		-14.5 psi		15 000 psi		34 800 psi	4	D	F	1)							
	0 8 700 psi		-14.5 psi		21 755 psi		52 200 psi	4	D	G	1)							
	0 14 500 psi		-14.5 psi		21 755 psi		72 520 psi	4		A								
Other version:			: Measuring range:	to psi					A							Н	1	
Output signal			J J															
		liary power 7	33 V DC (10 3	0 V DC for ATFX	devices)1)						0							
	ire system; auxilia			227							1)						
	e system; auxiliary										2							
			ry power 5 V DC ±	10%							3							
	tection (only 4		, pone. 5 v be ±															
None	(o.iiy	,										0						
	n protection Ex ia I	IIC T4 ¹⁾										1						
Electrical con										Н								
)3-A stuffing	hox thread M16 (w	vith coupling)1)									1					
Plug according to EN 175301-803-A, stuffing box thread M16 (with coupling) ¹⁾ M12 device plug according to IFC 61076-2-101													2					
M12 device plug according to IEC 61076-2-101											,							
Connection via permanently installed cable, 2 m (6.6 ft); not for "Intrinsic safety" type of protection)	3						
Quick-screw cable gland Quickon PG9; not for "Intrinsic safety" type of protection)	4						
Plug according to EN 175301-803-A, stuffing box thread 1/2"-14 NPT (with coupling) ¹⁾ Plug according to EN 175301-803-A, stuffing box thread PG11 (with coupling) ¹⁾												5						
		· ·		with coupling)1)									6					
-	nstalled cable, len	gth 5 m (16.4	4 Tt))	7					
Special design													9			N	1	

Pressure transmitters

Single-range transmitters / SITRANS P220

Selection and ordering data (continued)

	Article No.	Order code
SITRANS P220 pressure transmitter for gauge pressure, for high-pressure and cold applications, fully-welded version	7MF1567-	
	• • • • • • •	A • • •
Process connection		
G½" male according to EN 837-1 (½" BSP male) (standard for metric pressure ranges mbar, bar)	A	
G½" male and G1/8" female	В	
G¼" male according to EN 837-1 (¼" BSP male)	C	
7/16"-20 UNF male	D	
1/4"-18 NPT male (standard for pressure ranges inH ₂ O and psi) ¹⁾	E	
1/4"-18 NPT female	F	
½"-14 NPT male	G	
½"-14 NPT female	н	
7/16"-20 UNF female	J	
M20×1.5 male	P	
G¼" according to EN ISO 1179-2 (formerly DIN 3852 form E)	Q	
G½" according to EN ISO 1179-2 (formerly DIN 3852 form E)	R	
Special design	Z	P 1
Version		
Standard version ¹⁾		1

 $^{^{1)}}$ Order code E21 required for complete configurations with CRN and $_{\rm c}$ CSA $_{\rm us}$ Ex approval.

Options	Order code					
Add "-Z" to article number and specify order code.						
Quality inspection certificate (5-point characteristic curve test) according to IEC 62828-2 (not possible for measuring ranges $> 0 \dots 600$ bar/0 $\dots 8702$ psi)	C11					
Oxygen version, free of oil and degreased (not in combination with explosion protection version!)	E10					
With CRN and $_{c}$ CSA $_{us}$ Ex approval (only for measuring ranges 0 30 psi to 0 8 700 psi)	E21					

Pressure transmitters

Single-range transmitters / SITRANS P220

Technical specifications

SITRANS P220 for gauge pressure Area of application	
Mode of operation	
Measuring principle	Piezoresistive measuring cell (stainless steel diaphragm)
Measured variable	Gauge pressure
Input	
Measuring range	
Gauge pressure	
- Metric	2.5 1 000 bar (36 14 500 psi)
- US measuring range	30 14 500 psi
Output	
Current signal	4 20 mA
• Load	(U _B - 10 V)/0.02 A
Auxiliary power U _B	7 33 V DC (10 30 V for Ex)
Voltage signal	0 10 V DC
Load	≥ 10 kΩ
Auxiliary power U _B	12 33 V DC
· ·	
Current consumption	$<$ 7 mA at 10 k Ω
Radiometric output	10 90%
• Load	≥ 10 kΩ
Auxiliary power U _B	DC 5 V ± 10%
Current consumption	$<$ 7 mA at 10 k Ω
Characteristic curve	Linear rising
Measuring accuracy	
Measurement deviation at limit setting including hysteresis and reproducibility	Typical: 0.25% of measuring spanMaximum: 0.5% of measuring span
Step response time T ₉₉	< 5 ms
Long-term stability	
Lower range value and measuring span	0.25% of measuring span/year
Effect of ambient temperature	
Lower range value and measuring span	0.25%/10 K of measuring span
Influence of power supply	0.005%/V
Operating conditions	
Process temperature	-40 +120 °C (-40 +248 °F)
Ambient temperature	-25 +85 °C (-13 +185 °F)
Storage temperature	-50 +100 °C (-58 +212 °F)
Degree of protection according to IEC 60529	EN 175301-803-A
	IP67 with M12 device plug
	IP67 with cable
	IP67 with cable quick screw connection
Electromagnetic compatibility	• According to IEC 61326-1/-2/-3
	 According to NAMUR NE21 for ATEX devices only, and with a max. measure- ment error of ≤ 1%
Structural design	
	Approx. 0.090 kg (0.198 lbs)
Weight	
Weight Process connections	See dimension drawings
· ·	•
Process connections	• Plug according to EN 175301-803-A Form A with cable entry M16x1.5 or ½-14 NPT
Process connections	 Plug according to EN 175301-803-A Form A with cable entry M16x1.5 or ½-14 NPT or PG 11
Process connections	Plug according to EN 175301-803-A Form A with cable entry M16x1.5 or ½-14 NPT or PG 11 Device plug M12
Process connections	 Plug according to EN 175301-803-A Form A with cable entry M16x1.5 or ½-14 NPT or PG 11 Device plug M12 2 or 3-wire (0.5 mm²) cable (Ø ± 5.4 mm²)

Technical specifications (continued)

• Process connection	Stainless steel, mat. no. 1.4404 (SST 316 L)
	Stanless steer, mat. no. 1.4404 (331 316 L)
Material of non-wetted parts	
Enclosure	Stainless steel, mat. no. 1.4404 (SST 316 L)
Connector housing	Plastic
• Cable	PVC
Certificates and approvals	
Classification according to pressure equipment directive (PED 2014/68/EU)	For gases of fluid group 1 and liquids of fluid group 1; complies with requirements of article 4, paragraph 3 (sound engineering practice)
Lloyd's Register of Shipping (LR) ¹⁾	12/20010
Germanischer Lloyd (GL) ¹⁾	GL19740 11 HH00
American Bureau of Shipping (ABS) ¹⁾	ABS_11_HG 789392_PDA
Bureau Veritas (BV) ¹⁾	BV 271007A0 BV
Det Norske Veritas (DNV)1)	A 12553
Drinking water approval (ACS)1)	ACS 15 ACC NY 360
EAC ¹⁾	№ TC RU C-DE.ГБ05.В.00732 ОС НАНИО «ЦСВЭ»
CRN ²⁾	0F18659.5C
Underwriters Laboratories (UL)1)	
For USA and Canada	UL 20110217 - E34453
Worldwide	IEC UL DK 21845
Explosion protection	
Intrinsic safety "i" (only with current output)	Ex II 1/2 G Ex ia IIC T4 Ga/Gb Ex II 1/2 D Ex ia IIIC T125 °C Da/Db
EC type-examination certificate	SEV 10 ATEX 0146
Connection to certified intrinsically safe ohmic circuits with maximum values	$U_i \le DC \ 30 \ V; \ I_i \le 100 \ mA; \ P_i \le 0.75 \ W$
Effective internal inductance and capacity for versions with plugs according to EN 175301-803-A and M12	$L_i = 0$ nH; $C_i = 0$ nF
CSA ²⁾	70006348 Class I, Division I, Groups A, B, C&D Class II Division 1, Groups E, F and G, Class III Class I, Division 2, Groups A, B, C and D; Class II, Division 2, Groups F and G, Class III A/Ex ia IIC T4 Ga/Gb A/Ex ia IIIC T125°C Da/Db

- $^{\rm 1)}\,$ For variants with output signal 0 ... 5 V and radiometric output available soon.
 2) See ordering data for available versions.

Pressure transmitters


Single-range transmitters / SITRANS P220

Dimensional drawings

M12x1/Fixcon (0.7) Cable gland Quickon with or without cable

SITRANS P220, electrical connections, dimensions in mm (inch)

Dimensional drawings (continued)




SITRANS P220, process connections, dimensions in mm (inch)


Pressure transmitters

Single-range transmitters / SITRANS P220


Circuit diagrams




Connection with current output and plug according to EN 175301




Connection with current output and M12x1 device plug



Connection with current output and cable




Connection with current output and Quickon cable quick screw connection




Connection with voltage output, ratiometric output and plug according to EN 175301


Circuit diagrams (continued)



Connection with voltage output, ratiometric output and M12x1 device pluq




Connection with voltage output, ratiometric output and cable




Connection with voltage output, ratiometric output and Quickon fast cable termination

Device design with explosion protection: 4 to 20 mA

The grounding connection is conductively bonded to the transmitter enclosure.



Connection with current output and plug according to EN 175301 (Ex)



Connection with current output and M12x1 (Ex) device plug