


Overview



SITRANS P320/P420 pressure transmitters are digital pressure transmitters featuring extensive user-friendliness and high accuracy. The parameter assignment is performed using input buttons or the HART interface.

The comprehensive functionality makes for precise adjustment of the pressure transmitter to the requirements of the plant. Operation is very user-friendly in spite of the numerous setting options.

Due to their advanced diagnostic functionalities according to NAMUR NE107, the SITRANS P320/P420 pressure transmitters are very suitable for use in chemical plants. Thanks to the advanced diagnostic functions and the process value storage, the SITRANS P420 is "Ready for Digitization".

The "Remote Safety Handling" function saves customers significant amounts of time and money, because the SIL function can be switched on and validated remotely via SIMATIC PDM. This eliminates travel times and on-site operation via the local display or keyboard.

Parameter assignment using the HART protocol is very easy and quick thanks to the innovative EDD with integrated Quick Start wizard.

The transmitters can be equipped with various types of remote seals for special applications such as the measurement of highly viscous substances.

SITRANS P320/P420 pressure transmitters are available in various versions for measuring:

- Gauge pressure
- Absolute pressure
- Differential pressure
- Level
- Volume flow
- Mass flow

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Technical reference

Benefits

- Diagnostic functions in accordance with NAMUR recommendation NE107
- SIL devices developed according to IEC 61508
- SIL validation on the device or remotely with SIMATIC PDM
- Reduction of internal inductance for Ex applications to $L_I = 0$
- Step response time for pressure type $T_{63} = 105$ ms and for differential pressure type 135 ms.
- Minimal conformity error
- Very low temperature influence
- Very good long-term stability
- High quality and service life
- High reliability even under extreme chemical and mechanical loads
- For corrosive and non-corrosive gases, vapors and liquids
- Extensive diagnostics and simulation functions
- Separate replacement of measuring cell and electronics without recalibration
- Wetted parts made of high-grade materials (e.g., stainless steel, alloy, gold, Monel, tantalum)
- Infinitely adjustable spans from 0.01 bar to 700 bar (0.15 psi to 10153 psi)
- Convenient parameterization over 4 input buttons and HART interface

Application

SITRANS P320/P420 pressure transmitters can be used in industrial areas with extreme chemical and mechanical loads.

The pressure transmitters can be used in zone 1 or zone 0 with the corresponding Ex approval.

The pressure transmitters can be equipped with various designs of remote seals for special applications such as the measurement of highly viscous substances.

The pressure transmitter can be operated locally over 4 input buttons or programmed externally over HART interface.

Pressure transmitters for gauge pressure

Measured variable:

- Gauge pressure of corrosive and non-corrosive gases, vapors and liquids.

Measuring span (infinitely adjustable)

- For SITRANS P320/P420 with HART: 0.01 bar to 700 bar (0.15 psi to 10153 psi)

There are two series:

- Gauge pressure series

- Differential pressure series

Pressure transmitters for absolute pressure

Measured variable:

- Absolute pressure of corrosive and non-corrosive gases, vapors and liquids.

Measuring span (infinitely adjustable)

- For SITRANS P320/P420 with HART: 8.3 mbar a to 160 bar a (0.12 to 2 321 psi a)

There are two series:

- Gauge pressure series

- Differential pressure series

Pressure transmitters for differential pressure and flow

Measured variables:

- Differential pressure

- Small positive or negative overpressure

- Flow $q \sim \sqrt{\Delta p}$ (together with a primary differential pressure transducer (see section "Flowmeters"))

Measuring span (infinitely adjustable)

- For SITRANS P320/P420 with HART: 1 mbar to 160 bar (0.0145 to 2 321 psi)

Pressure transmitters for level

Measured variable:

- Level of corrosive and non-corrosive liquids in open and closed vessels.

Measuring span (infinitely adjustable)

- For SITRANS P320/P420 with HART: 25 mbar to 5 bar (0.363 to 72.5 psi)

Type of the mounting flange:

- EN 1092-1 flanges


- ASME B16.5 flanges

- J.I.S. flanges

- Diverse range of sealing surface forms available

Design

Depending on the customer-specific order, the device comprises different parts.



Device front view

- The electronics enclosure is made of die cast aluminum or precision cast stainless steel.
- The enclosure has a removable cover at the front and the back.
- Depending on the device design, the front cover (2) may be designed with a glass pane.
- The cable inlet (8) to the electrical terminal compartment is at the side; either the left or right-hand one can be used. The unused opening is closed with a blanking plug (15).
- The ground terminal (13) is located on the side.
- The electrical terminal compartment (11) for the auxiliary power and shield is accessible when you remove the back cover (10).
- The measuring cell with process connection (6) is located in the bottom part of the enclosure. The measuring cell is prevented from rotating by a locking screw (5).
- Thanks to the modular design of the pressure transmitter, the measuring cell and application electronics or terminal compartment can be replaced if required.
- The button cover (1) is located on the upper face of the enclosure. The nameplate with general information is located on the cover over the buttons.

Nameplates

Nameplate


The nameplate with the article no. and other important information, such as design details and technical data, is located on the cover over the buttons.

Pressure measurement

Pressure transmitters


for applications with advanced requirements / SITRANS P320/420 / Technical reference

Design (continued)



Certification label with approval information

The certification label with approval information is located on the front of the enclosure.

Design (continued)Tag plate

The tag plate is fastened with a wire under the front cover.

Nameplate with information on the remote seals


The nameplate with information on the remote seals is located on the back of the enclosure.

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Technical reference

Design (continued)



Function

Adjustable parameters and diagnostics

SITRANS P320/P420 with HART communication

Parameters	Input buttons	SITRANS P320	SITRANS P420
Application, measurement type	x	x	x
Adjusting lower range value/upper range value	x	x	x
Setting lower range value/upper range value	x	x	x
Electrical damping	x	x	x
Zero adjustment	x	x	x
Fault current	x	x	x
Saturation limits	x	x	x
Scaling of the display	x	x	x
Characteristic curve selection	x	x	x
Temperature unit	x	x	x
Button lock	x	x	x
Change user PIN	x	x	x
Functional safety	x	x	x
Loop test	x	x	x
Start view	x	x	x
Pressure reference	x	x	x
Reset	x	x	x
Diagnostics and trend log			
Min/max pointer	-	x	x
Limit monitoring	-	2	2
Event counter (overrun/undershoot)	-	2	2
Maintenance and service timer	-	x	x
Trend log	-	-	2, max. 1 500 values
Diagnostic log	-	x	x
Parameters change log	-	-	x

Available physical units of display for SITRANS P320/P420

Physical variable	Physical units
Pressure (can also be preset in the factory)	Pa, MPa, kPa, hPa, bar, mbar, psi, g/cm ² , kg/cm ² , kgf/cm ² , inH ₂ O, inH ₂ O (4 °C), ftH ₂ O, mmH ₂ O, mmH ₂ O (4 °C), mH ₂ O (4 °C), mmHg, inHg, atm, torr
Level (height data)	m, cm, mm, ft, in
Volumes (fill level)	m ³ , l, hl, in ³ , ft ³ , yd ³ , gal, gal (UK), bu, bbl, bbl (US), SCF, Nm ³ , NI
Volume (flow)	m ³ /sec, m ³ /h, m ³ /d, l/sec, l/min, l/h, MI/d, ft ³ /sec, ft ³ /h, ft ³ /d, SCF/min, SCF/h, NI/h, Nm ³ /hgal/sec, gal/min, gal/h, gal/d, Mgal/d, gal (UK)/sec, gal (UK)/min, gal (UK)/h, gal (UK)/d, bbl/sec, bbl/min, bbl/h, bbl/d,
Mass (flow)	Kg/sec, kg/min, kg/h, kg/d, g/sec, g/min, g/l, t/min, t/h, t/d, lb/sec, lb/min, lb/h, lb/d, ton/min, ton/h, ton/d, ton (UK)/h, ton (UK)/d
Temperature	°C, °F
Other	%, mA, free text max. 12 characters

For more device information and technical specifications, refer to the individual device versions.

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge pressure (pressure series)

Selection and ordering data

	Article No.
Pressure transmitters for gauge pressure (pressure series)	
SITRANS P320	7MF030
SITRANS P420	7MF040
Click the article number for online configuration in the PIA Life Cycle Portal.	
Communication	
HART, 4 ... 20 mA	0
PROFIBUS PA	1
FOUNDATION Fieldbus (FF)	2
Measuring cell filling	
Silicone oil	1
Inert liquid	3
Neobee oil	4
Maximum measuring span	
250 mbar (3.6 psi)	F
1 000 mbar (14.5 psi)	J
4 000 mbar (58 psi)	N
16 bar (232 psi)	Q
63 bar (914 psi)	T
160 bar (2 321 psi)	V
400 bar (5 802 psi)	W
700 bar (10 153 psi)	X
Process connection	
External thread M20 x 1.5	B
External thread G½ (EN 837-1)	D
Internal thread ½-14 NPT	E
External thread ½-14 NPT	F
Oval flange, fastening thread: 7/16-20 UNF (IEC 61518)	G
Oval flange, fastening thread: M10 (DIN 19213)	H
Oval flange, fastening thread: M12 (DIN 19213)	J
Version for diaphragm seal pressure	U
Material of wetted parts: Process connection, seal diaphragm	
Stainless steel 316L/1.4404, stainless steel 316L/1.4404	0
Stainless steel 316L/1.4404, alloy C276/2.4819	1
Alloy C22/2.4602, alloy C276/2.4819	2
Stainless steel 316L/1.4404, stainless steel 316L/1.4404 gold-plated	7
Material of non-wetted parts	
Die-cast aluminum	1
Stainless steel precision casting CF3M/1.4409 similar to 316L	2
Enclosure	
Dual chamber device	5
Type of protection	
Without Ex	A
Intrinsic safety	B
Flameproof enclosure	C
Flameproof enclosure, intrinsic safety	D
Dust protection by enclosure Zone 21/22 (DIP), increased safety Zone 2	L
Intrinsic safety, dust protection by enclosure Zone 20/21/22 (DIP), increased safety Zone 2	M
Combination of options B, C and L (Zone model)	S
Combination of options B, C and L (Zone model, Class Division)	T
Electrical connections/cable entries	
Thread for cable gland: Cable gland must be ordered separately as option (Axx)	
• 2 x M20 x 1.5	F
• 2 x ½-14 NPT	M
Local operation/display	
Without local display (lid closed)	0
With local display (lid closed)	1
With local display (lid with glass pane)	2

Selection and ordering data (continued)

Options Add "Z" to article no., add order code and plain text or entry from drop-down list.	Order code
Cable glands included	
Plastic	A00
Metal	A01
Stainless steel	A02
Stainless steel 316L/1.4404	A03
CMP, for XP devices	A10
CAPRI ADE 4F, CuZn, cable inner diameter 7 ... 12 mm, cable outer diameter 10 ... 16 mm	A11
CAPRI ADE 4F, stainless steel, cable inner diameter 7 ... 12 mm, cable outer diameter 10 ... 16 mm	A12
Sealing plug included, plastic	A20
Sealing plug included, metal	A21
Sealing plug included, stainless steel	A22
Sealing plug included, stainless steel 316L/1.4404	A23
Device plug Han mounted left	
Device plug Han 7D (plastic, straight)	A30
Device plug Han 7D (plastic, angled)	A31
Device plug Han 7D (metal, straight)	A32
Device plug Han 7D (metal, angled)	A33
Device plug Han 8D (plastic, straight)	A34
Device plug Han 8D (plastic, angled)	A35
Device plug Han 8D (metal, straight)	A36
Device plug Han 8D (metal, angled)	A37
Cable socket included	
Plastic, for device plug Han 7D and Han 8D	A40
Metal, for device plug Han 7D and Han 8D	A41
Device plug M12 mounted left	
Stainless steel, without cable socket	A62
Stainless steel, with cable socket	A63
Cable entry/device plug mounting	
2 x sealing plugs M20 x 1.5, IP66/68 installed on both sides	A90
2 x sealing plugs 1/2-14 NPT, IP66/68 installed on both sides	A91
Cable gland/device plug mounted left	A97
Cable gland/device plug mounted right	A99
Nameplate labeling (standard labeling: English, unit bar)	
German (bar)	B11
French (bar)	B12
Spanish (bar)	B13
Italian (bar)	B14
Chinese (bar)	B15
Russian (bar)	B16
English (psi)	B20
English (Pa)	B30
Chinese (Pa)	B35
Certificates	
Quality inspection certificate, 5-point factory calibration (IEC 62828-2)	C11
Inspection certificate (EN 10204-3.1) - Material of pressurized and wetted parts	C12
Factory certificate - NACE (MR 0103-2012 and MR 0175-2009)	C13
Factory certificate (EN 10204-2.2) - Wetted parts	C14
Inspection certificate (EN 10204-3.1) - PMI test of pressurized and wetted parts	C15

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge pressure (pressure series)

Selection and ordering data (continued)

Options	Order code
Add "Z" to article no., add order code and plain text or entry from drop-down list.	
Certificates for functional safety	
Functional Safety (IEC 61508) - SIL2/3	C20
Device options	
PDF file with device settings	D10
Double layer coating (epoxy resin and polyurethane) 120 µm of enclosure and lid	D20
FVMQ enclosure sealing	D21
IP66/IP68 degree of protection (not for device plug M12 and Han)	D30
Unlabeled TAG plate	D40
Without labeling of the measuring range on the TAG plate	D41
Stainless steel Ex plate 1.4404/316L	D42
Oversupply protection up to 6 kV (internal)	D70
Oversupply protection up to 6 kV (external)	D71
Labels on transport packaging (provided by customer)	D90
General approval without Ex approval	
Worldwide (CE, UKCA, RCM) except EAC, FM, CSA, KCC	E00
Worldwide (CE, UKCA, RCM, EAC, FM, CSA, KCC)	E01
CSA (USA and Canada)	E06
EAC	E07
FM	E08
KCC	E09
Explosion protection approvals	
ATEX (Europe)	E20
CSA (USA and Canada) ¹⁾	E21
FM (USA and Canada) ¹⁾	E22
IECEx (Worldwide)	E23
EACEx (GOST-R, -K, -B)	E24
INMETRO (Brazil)	E25
KCs (Korea)	E26
NEPSI (China)	E27
PESO (India)	E28
UKR Sepro (Ukraine)	E30
UKEX (United Kingdom)	E33
ATEX (Europe), IECEx (Worldwide) and UKEX (UK)	E47
CSA (Canada) and FM (USA) ¹⁾	E48
ATEX (Europe) and IECEx (Worldwide) + CSA (Canada) and FM (USA) ¹⁾	E49
Marine approvals	
DNV-GL (Det Norske Veritas/Germanischer Lloyd)	E50
LR (Lloyds Register)	E51
BV (Bureau Veritas)	E52
ABS (American Bureau of Shipping)	E53
RMR (Russian Maritime Register)	E55
KR (Korean Register of Shipping)	E56
RINA (Registro Italiano Navale)	E57
CCS (China Classification Society)	E58
Country-specific approvals	
CRN approval Canada (Canadian Registration Number)	E60
Special approvals	
Oxygen application (with inert liquid, max. 160 bar (2 320 psi) at 100 °C (212 °F))	E80
Dual Seal	E81

Selection and ordering data (continued)

Options Add "Z" to article no., add order code and plain text or entry from drop-down list.	Order code
WRC/WRAS (drinking water); only with process flange O-rings made of EPDM	E83
NSF61 (drinking water)	E84
ACS (drinking water)	E85
Mounting bracket	
Steel, zinc-plated	H01
Stainless steel 1.4301/304	H02
Stainless steel 1.4404/316L	H03
Flange connections with flange EN 1092-1	
With flange adapter G½ Form B1	
• DN 25 PN 40, stainless steel 1.4571/316Ti	J80
• DN 50 PN 40, stainless steel 1.4571/316Ti	J81
• DN 80 PN 40, stainless steel 1.4571/316Ti	J82
With water trap G½ form B1	
• DN 25 PN 40, stainless steel 1.4571/316Ti	J83
• DN 50 PN 40, stainless steel 1.4571/316Ti	J84
• DN 80 PN 40, stainless steel 1.4571/316Ti	J85
• DN 25 PN 100, stainless steel 1.4571/316Ti	J86
Process flanges, gaskets (instead of standard gaskets FKM (FPM))	
Gasket (EN 837-1) material Fe (soft iron)	K60
Gasket (EN 837-1) material 1.4571	K61
Gasket (EN 837-1) material Cu	K62
Process connection	
Process connection external thread G½, bore hole 11 mm	K80
Shut-off valves, valve manifolds	
With mounted valve manifold 7MF9011-4EA, process connection at transmitter G½ shank, PTFE sealing ring and pressure test certified in factory certificate (EN 10204-2.2)	T02
With mounted valve manifold 7MF9011-4FA, process connection at transmitter internal thread ½-14 NPT, sealing tape. With PTFE sealing ring and pressure test certified in factory certificate (EN 10204-2.2)	T03
With mounted valve manifold 7MF9411-5AA, process connection at transmitter oval flange with PTFE sealing ring, steel fixing screws, pressure test certified in factory certificate (EN 10204-2.2)	T05
With mounted valve manifold 7MF9411-5AA, process connection at transmitter oval flange with PTFE sealing ring, stainless steel fixing screws, pressure test certified in factory certificate (EN 10204-2.2)	T06
Device settings	
Measuring span: Lower range value (max. 5 characters), upper range value (max. 5 characters), unit [mbar, bar, kPa, MPa, psi, ...], example: -0.5 ... 10.5 psi	Y01
TAG (on stainless steel plate and device parameters, max. 32 characters)	Y15
Measuring point description (on stainless steel plate and device parameters, max. 32 characters)	Y16
TAG short (device parameters, max. 8 characters)	Y17
Local display: [Pressure, Percent], reference [None, Absolute, Gauge], example: Pressure gauge	Y21
Local display: Scaling with standard units [m^3/s , l/s , m, inch, ...]; example 1 ... 5 m	Y22
Local display: Scaling with user-specific units (max. 12 characters), example 1 ... 5 m	Y23
Set PROFIBUS PA device address (1 ... 126)	Y25

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge pressure (pressure series)

Selection and ordering data (continued)

Options	Order code
Add "Z" to article no., add order code and plain text or entry from drop-down list.	
Saturation limits instead of 3.8 ... 20.5 mA, example: 3.8 ... 22.0 mA	Y30
Fault current instead of 3.6 mA [22.5 mA, 22.8 mA]	Y31
Damping in seconds instead of 2 s (0.0 ... 100.0 s)	Y32
ID number of special design	Y99

¹⁾ Explosion protection acc. to FM/CSA: suitable for installation according to NEC 500/505.

Technical specifications

SITRANS P320/SITRANS P420 for gauge pressure (pressure series)

Input	Gauge pressure	Measuring span	Max. permissible operating pressure MAWP (PS)	Maximum permissible test pressure
Measured variable				
Measuring span (continuously adjustable) or measuring range, max. permissible operating pressure (in accordance with Pressure Equipment Directive 2014/68/EU) and max. permissible test pressure (pursuant to DIN 16086) (for oxygen measurement, max. 100 bar/10 MPa/1450 psi and 60 °C (140 °F) ambient temperature/medium temperature)				
	0.01 ... 1 bar 1 ... 100 kPa 0.15 ... 14.5 psi	8.3 ... 250 mbar 0.83 ... 25 kPa 0.12 ... 3.6 psi	4 bar 0.4 MPa 58 psi	6 bar 0.6 MPa 87 psi
	0.04 ... 4 bar 4 ... 400 kPa 0.58 ... 58 psi		20 bar 2 MPa 290 psi	30 bar 3 MPa 435 psi
	0.16 ... 16 bar 0.016 ... 1.6 MPa 2.3 ... 232 psi		45 bar 4.5 MPa 652 psi	70 bar 7 MPa 1015 psi
	0.63 ... 63 bar 0.063 ... 6.3 MPa 9.1 ... 914 psi		80 bar 8 MPa 1160 psi	120 bar 12 MPa 1740 psi
	1.6 ... 160 bar 0.16 ... 16 MPa 23 ... 2321 psi		240 bar 24 MPa 3481 psi	360 bar 36 MPa 5221 psi
	4 ... 400 bar 0.4 ... 40 MPa 58 ... 5802 psi		400 bar 40 MPa 5802 psi	600 bar 60 MPa 8702 psi
	7 ... 700 bar 0.7 ... 70 MPa 102 ... 10153 psi		800 bar 80 MPa 11603 psi	800 bar 80 MPa 11603 psi
Measuring limits				
• Lower measuring limit				For 250 mbar/25 kPa/3.6 psi measuring cells, the lower measuring limit is 750 mbar a/75 kPa a/10.8 psi a. The measuring cell is vacuum-resistant up to 30 mbar a/3 kPa a/0.44 psi a.
- Measuring cell with silicone oil filling				30 mbar a/3 kPa a/0.44 psi a
- Measuring cell with inert oil				30 mbar a/3 kPa a/0.44 psi a
- Measuring cell with FDA-compliant oil				100 mbar a/10 kPa a/1.45 psi a
• Upper measuring limit				100% of the max. measuring span (for oxygen measurement max. 100 bar/10 MPa/1450 psi and 60 °C (140 °F) ambient temperature/medium temperature)
• Lower range value				Between the measuring limits (continuously adjustable)
Output	HART			
Output signal				
• Lower saturation limit (continuously adjustable)	4 ... 20 mA			
• Upper saturation limit (continuously adjustable)	3.55 mA, factory set to 3.8 mA			
• Ripple (without HART communication)	22.8 mA, factory-set to 20.5 mA or optionally 22.0 mA			
Adjustable damping	$I_{pp} \leq 0.5\%$ of max. output current	0 ... 100 s, continuously adjustable over remote operation		
		0 ... 100 s, in increments of 0.1 s, adjustable over display		

Technical specifications (continued)

SITRANS P320/SITRANS P420 for gauge pressure (pressure series)		
• Current simulator	3.55 ... 22.8 mA	
• Failure signal	3.55 ... 22.8 mA (factory set to 3.55 mA)	
Load	Resistance R [Ω]	
• Without HART communication	$R = (U_H - 10.5 \text{ V}) / 22.8 \text{ mA}$, U_H : Auxiliary power in V	
• With HART communication	$R = 230 \dots 1100 \Omega$	
Characteristic curve	• Linearly increasing or linearly decreasing • Linear increase or decrease or according to the square root (only for differential pressure and flow)	
Physical bus	-	
Polarity-independent	-	
Measuring accuracy		
Reference conditions	• According to IEC 62828-1 • Rising characteristic curve • Lower range value 0 bar/kPa/psi • Seal diaphragm stainless steel • Measuring cell with silicone oil filling • Room temperature 25 °C (77 °F)	
Conformity error at limit point setting, including hysteresis and repeatability		
Measuring span ratio r (spread, Turn-Down)	$r = \text{max. measuring span}/\text{set measuring span and nominal measuring range}$	
• Linear characteristic curve		
- 250 mbar/25 kPa/3.6 psi	$r \leq 1.25:$ $\leq 0.075\%$ (SITRANS P320) $\leq 0.065\%$ (SITRANS P420)	
- 1 bar/100 kPa/14.5 psi 4 bar/400 kPa/58 psi 16 bar/1.6 MPa/232 psi 63 bar/6.3 MPa/914 psi 160 bar/16 MPa/2321 psi	$1.25 < r \leq 30:$ $r \leq 5:$ $\leq (0.008 \cdot r + 0.065)\%$ $\leq 0.065\%$ (SITRANS P320) $\leq 0.04\%$ (SITRANS P420)	
- 400 bar/40 MPa/5802 psi 700 bar/70 MPa/10152 psi	$5 < r \leq 100:$ $r \leq 5:$ $\leq (0.004 \cdot r + 0.045)\%$ $\leq 0.075\%$ (SITRANS P320) $\leq (0.005 \cdot r + 0.05)\%$ (SITRANS P320)	
- 5 < r ≤ 100:	$\leq 0.075\%$ (SITRANS P420) $\leq (0.005 \cdot r + 0.05)\%$ (SITRANS P420)	
Influence of ambient temperature in % per 28 °C (50 °F)		
• 250 mbar/25 kPa/3.6 psi	$\leq (0.16 \cdot r + 0.1)\%$	
• 1 bar/100 kPa/14.5 psi	$\leq (0.05 \cdot r + 0.1)\%$	
• 4 bar/400 kPa/58 psi 16 bar/1.6 MPa/232 psi 63 bar/6.3 MPa/914 psi 160 bar/16 MPa/2321 psi 400 bar/40 MPa/5802 psi	$\leq (0.025 \cdot r + 0.125)\%$	
• 700 bar/70 MPa/10152 psi	$\leq (0.08 \cdot r + 0.16)\%$	
Long-term stability at ±30 °C (± 54 °F)		
• 250 mbar/25 kPa/3.6 psi	$\leq (0.25 \cdot r)\%$ per year	
• 1 bar/100 kPa/14.5 psi	In 5 years $\leq (0.25 \cdot r)\%$ In 10 years $\leq (0.35 \cdot r)\%$	
• 4 bar/400 kPa/58 psi 16 bar/1.6 MPa/232 psi 63 bar/6.3 MPa/914 psi 160 bar/16 MPa/2321 psi 400 bar/40 MPa/5802 psi	In 5 years $\leq (0.125 \cdot r)\%$ In 10 years $\leq (0.15 \cdot r)\%$	
• 700 bar/70 MPa/10152 psi	In 5 years $\leq (0.25 \cdot r)\%$ In 10 years $\leq (0.35 \cdot r)\%$	
Step response time T_{63} (without electrical damping)	$\leq 0.105 \text{ s}$	
Effect of mounting position (in pressure per change of angle)	$\leq 0.05 \text{ mbar}/0.005 \text{ kPa}/0.000725 \text{ psi}$ per 10° incline (zero offset is possible with position error compensation)	
Effect of auxiliary power (in % per voltage change)	0.005% per 1 V	

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge pressure (pressure series)

Technical specifications (continued)

SITRANS P320/SITRANS P420 for gauge pressure (pressure series)

Operating conditions

Medium temperature

- Measuring cell with silicone oil filling -40 ... +100 °C (-40 ... +212 °F)
- Measuring cell with inert oil -40 ... +100 °C (-40 ... +212 °F)
- 1 bar/100 kPa/14.5 psi
4 bar/400 kPa/58 psi
16 bar/1.6 MPa/232 psi
63 bar/6.3 MPa/914 psi
- 160 bar/16 MPa/2321 psi
400 bar/40 MPa/5802 psi
700 bar/70 MPa/10152 psi
- Measuring cell with FDA-compliant oil -10 ... +100 °C (14 ... +212 °F)

Ambient conditions

- Ambient temperature/enclosure Observe the temperature class in hazardous areas.

- Measuring cell with silicone oil filling -40 ... +85 °C (-40 ... +185 °F)
- Measuring cell with inert oil for gauge pressure measuring cells:

1 bar/100 kPa/14.5 psi
4 bar/400 kPa/58 psi
16 bar/1.6 MPa/232 psi
63 bar/6.3 MPa/914 psi

- Measuring cell with inert oil -40 ... +85 °C (-40 ... +185 °F)
- Measuring cell with FDA-compliant oil -10 ... +85 °C (14 ... +185 °F)

- Display -20 ... +80 °C (-4 ... +176 °F)

- Storage temperature -50 ... +85 °C (-58 ... +185 °F) (with FDA-compliant oil: -20 ... +85 °C (-4 ... +185 °F))

- Climatic class in accordance with IEC 60721-3-4 4K4H

- Degree of protection

- According to IEC 60529 IP66, IP68

- According to NEMA 250 Type 4X

- Electromagnetic compatibility

- Emitted interference and interference immunity According to IEC 61326 and NAMUR NE 21

Structural design

Weight

- Aluminum enclosure: Approx. 1.8 kg (3.9 lbs)
- Stainless steel enclosure: Approx. 3.8 kg (8.3 lbs)

Material

- Material of wetted parts

- Process connection Stainless steel, material no. 1.4404/316L or Alloy C22, material no. 2.4602

- Oval flange Stainless steel, mat. no. 1.4404/316L

- Seal diaphragm Stainless steel, material no. 1.4404/316L or Alloy C276, material no. 2.4819

- Material of non-wetted parts

- Electronics enclosure

- Low-copper die-cast aluminum GD-AlSi 12 or stainless steel precision casting, mat. no. 1.4409/ CF-3M
- Standard: Powder coating with polyurethane
Option: 2 coats: Coat 1: Epoxy-based; coat 2: Polyurethane
- Coating: The layer structure and thickness correspond to EN ISO 12944 Corrosion Class C3-M (for standard transmitter) and C5-H (for transmitter with double layer coating)
- Stainless steel nameplate (1.4404/316L)

Technical specifications (continued)

SITRANS P320/SITRANS P420 for gauge pressure (pressure series)	
- Mounting bracket	Zinc-plated steel or stainless steel
Process connection	<ul style="list-style-type: none"> • Connection shank G1/2A according to EN 837-1 • Female thread 1/2-14 NPT • Oval flange (PN 160 (MWP 2320 psi g)) with fastening thread: <ul style="list-style-type: none"> - 7/16-20 UNF according to EN 61518 - M10 according to DIN 19213 • Oval flange (PN 420 (MWP 2320 psi g)) with fastening thread: <ul style="list-style-type: none"> - 7/16-20 UNF according to EN 61518 - M12 according to DIN 19213 • Male thread M20 x 1.5 and 1/2-14 NPT
Electrical connection	<p>Cable entry via the following screw glands:</p> <ul style="list-style-type: none"> • M20 x 1.5 • 1/2-14 NPT • Device plug Han 7D/Han 8D¹⁾ • Device plug M12
Displays and controls	
Buttons	4 buttons for operation directly on the device
Display	<ul style="list-style-type: none"> • With or without integrated display (optional) • Lid with inspection window (optional)
Auxiliary power U_H	
Terminal voltage on pressure transmitter	10.5 ... 45 V DC 10.5 ... 30 V DC in intrinsically safe mode
Ripple	U _{SS} ≤ 0.2 V (47 ... 125 Hz)
Noise	U _{eff} ≤ 1.2 mV (0.5 ... 10 kHz)
Auxiliary power	–
Separate supply voltage	–
Certificates and approvals	
Classification according to pressure equipment directive (PED 2014/68/EU)	For gases of fluid group 1 and liquids of fluid group 1; complies with requirements of article 4, paragraph 3 (sound engineering practice)
Drinking water	
• WRAS (England)	No.: 1903094 (option E83)
• ACS (France)	No.: 18 ACC LY 277 (option E85)
• NSF (USA)	No.: 20180920-MH61350 (option E84)
CRN (Canada)	No.: 0F9863.5C (option E60)
Explosion protection acc. to NEPSI (China)	No.: GYJ19.1058X (option E27)
Explosion protection acc. to INMETRO (Brazil)	No.: BRA-18-GE-0035X (option E25)
Explosion protection	
• Intrinsic safety "i"	
- Marking	II 1/2 G Ex ia/b IIC T4/T6 Ga/Gb
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +55 °C (-40 ... +131 °F) temperature class T6
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Connection	To certified intrinsically safe circuits with peak values: U _i = 30 V, I _i = 101 mA, P _i = 760 mW U _i = 29 V, I _i = 110 mA, P _i = 800 mW L _i = 0.24 µH/C _i = 3.29 nF
- Effective internal inductance/capacitance	
• Flameproof enclosure "d"	Ex II 1/2 G Ex ia/db IIC T4/T6 Ga/Gb
- Marking	
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Connection	To a circuit with the operating values: U _n = 10.5 ... 45 V, 4 ... 20 mA

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge pressure (pressure series)

Technical specifications (continued)

SITRANS P320/SITRANS P420 for gauge pressure (pressure series)

• Dust explosion protection for Zones 21, 22	
- Marking	Ex II 2D Ex tb IIIC T120 °C Db Ex II 3D Ex tc IIIC T120 °C Dc
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F)
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F)
- Max. surface temperature	120 °C (248 °F)
- Connection	To a circuit with the operating values: $U_n = 10.5 \dots 45 V$, $4 \dots 20 mA$
• Dust explosion protection for Zones 20, 21, 22	
- Marking	Ex II 1D Ex ia IIIC T120 °C Da Ex II 2D Ex ib IIIC T120 °C Db
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F)
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F)
- Connection	To certified intrinsically safe circuits with peak values: $U_i = 30 V$, $I_i = 101 mA$, $P_i = 760 mW$ $U_i = 29 V$, $I_i = 110 mA$, $P_i = 800 mW$ $L_i = 0.24 \mu H/C_i = 3.29 nF$
- Effective internal inductance/capacitance	
• Type of protection for Zone 2	
- Marking	Ex II 3G Ex ec IIC T4/T6 Gc
- Permissible ambient temperature "ec"	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +40 °C (-40 ... +104 °F) temperature class T6
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- "ec" connection	To a circuit with the operating values: $U_n = 10.5 \dots 30 V$, $4 \dots 20 mA$
• Explosion protection acc. to FM	Available soon
- Marking (XP/DIP) or IS; NI; S	CL I, DIV 1, GP ABCD T4 ... T6; CL II, DIV 1, GP EFG; CL III; Ex ia IIC T4 ... T6: CL I, DIV 2, GP ABCD T4 ... T6; CL II, DIV 2, GP FG; CL III
• Explosion protection according to CSA	Available soon
- Marking (XP/DIP) or (IS)	CL I, DIV 1, GP ABCD T4 ... T6; CL II, DIV 1, GP EFG; CL III; Ex ia IIC T4 ... T6: CL I, DIV 2, GP ABCD T4 ... T6; CL II, DIV 2, GP FG; CL III
NAMUR recommendations	
• NE 06	Standardized Electrical Signals and Questions Relating to Engineering Technology
• NE 21	Electromagnetic Compatibility (EMC) of Industrial Process and Laboratory Control Equipment
• NE 23	Extra Low Voltage Circuits with Safe Separation
• NE 43	Standardization of the Signal Level for the Failure Information of Digital Transmitters
• NE 53	Software and Hardware of Field Devices and Signal Processing Devices with Digital Electronics
• NE 80	The Application of the Pressure Equipment Directive to Process Control Devices
• NE 105	Specifications for Integrating Fieldbus Devices in Engineering Tools for Field Devices
• NE 107	Self-Monitoring and Diagnosis of Field Devices
• NE 131	NAMUR Standard Device - Field Devices for Standard Applications

¹⁾ Han 8D is identical to Han 8U.

Communication

HART	230 ... 1 100 Ω
Protocol	HART 7
Software for computer	SIMATIC PDM
PROFIBUS PA	
Simultaneous communication with master class 2 (max.)	4
The address can be set using	Configuration tool or local operation (default setting address 126)
Cyclic data usage	
• Output byte	≤ 35 (7 measured values)
• Input byte	0, 1, or 2 (register operation mode and reset function for dosing)

Technical specifications (continued)


Communication	
Internal preprocessing	
Device profile	PROFIBUS PA Profile Version 4.01 Class B. Cyclic data usage compatible with version 3.XX
Number of function blocks	7
• Analog input	
- Adaptation to user-specific process variable	Yes, linearly rising or falling characteristic curve
- Electrical damping adjustable	0 ... 100 s
- Simulation function	Output/input
- Limit monitoring	Yes, one upper and lower warning limit and one alarm limit respectively
• Register (totalizer)	Can be reset, preset, optional direction of counting, simulation function of register output
- Limit monitoring	One upper and lower warning limit and one alarm limit respectively
• Physical block	1
Transducer blocks	1
• Pressure transducer block	
- Can be calibrated by applying two pressures	Yes
- Monitoring of sensor limits	Yes
- Specification of a vessel characteristic curve with	Max. 30 nodes
- Square-rooted characteristic curve for flow measurement	Yes
- Tank characteristic curve for volume measurement	Yes
- Low flow cut-off and implementation point of square-root extraction	Parameterizable
- Simulation function for measured pressure value and sensor temperature	Constant value or by means of parameterizable ramp function
FOUNDATION Fieldbus	
Device profile	FF ITK 6
Function blocks	3 function blocks analog input, 1 function block PID
• Analog input	
- Adaptation to user-specific process variable	Yes, linearly rising or falling characteristic curve
- Electrical damping adjustable	0 ... 100 s
- Simulation function	Output/input (can be locked within the device with a bridge)
- Failure mode	Parameterizable (last good value, substitute value, incorrect value)
- Limit monitoring	Yes, one upper and lower warning limit and one alarm limit respectively
- Square-rooted characteristic curve for flow measurement	Yes
• PID	Standard FOUNDATION Fieldbus function block
• Physical block	1 resource block
Transducer blocks	1 transducer block Pressure with calibration, 1 transducer block LCD
• Pressure transducer block	
- Can be calibrated by applying two pressures	Yes
- Monitoring of sensor limits	Yes
- Simulation function: pressure measurement, sensor temperature and electronics temperature	Constant value or by means of parameterizable ramp function

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge pressure (pressure series)

Dimensional drawings



SITRANS P320/P420 pressure transmitter for gauge pressure (pressure series), dimensions in mm (inch)

Pressure measurement**Pressure transmitters****for applications with advanced requirements / SITRANS P320/420 / Gauge pressure (differential pressure series)****Selection and ordering data**

	Article No.
Pressure transmitters for gauge pressure (differential pressure series)	
SITRANS P320	7MF031
SITRANS P420	7MF041
Click the article number for online configuration in the PIA Life Cycle Portal.	
Communication	
HART, 4 ... 20 mA	0
PROFIBUS PA	1
FOUNDATION Fieldbus (FF)	2
Measuring cell filling	
Silicone oil	1
Inert filling liquid	3
Maximum measuring span	
20 mbar (8.037 inH ₂ O)	B
60 mbar (24.11 inH ₂ O)	D
250 mbar (1005 inH ₂ O)	G
600 mbar (241.1 inH ₂ O)	H
1 600 mbar (643 inH ₂ O)	M
5 000 mbar (2009 inH ₂ O)	P
30 bar (435 psi)	R
160 bar (2 320 psi)	Y
Process connection	
Oval flange, fastening thread: 7/16-20 UNF (IEC 61518)	L
Oval flange, fastening thread: M10 (PN 160), (DIN 19213)	M
Oval flange, fastening thread: 7/16-20 UNF (IEC 61518) with lateral ventilation	N
Oval flange, fastening thread: M10 (PN 160) (DIN 19213) with lateral ventilation	P
Material of wetted parts: Process connection, seal diaphragm	
Stainless steel 316L/1.4404, stainless steel 316L/1.4404, process flange stainless steel 316/1.4408	0
Stainless steel 316L/1.4404, alloy C276/2.4819, process flange stainless steel 316/1.4408	1
Alloy C22/2.4602, alloy C276/2.4819, process flange stainless steel 316/1.4408	2
Tantalum/tantalum, process flange stainless steel 316/1.4408 (not in combination with maximum measuring span 20 mbar (0.29 psi) and 60 mbar (0.87 psi))	4
Monel 400/2.4360, Monel 400/2.4360, process flange stainless steel 316/1.4408 (not in combination with maximum measuring span 20 mbar (0.29 psi) and 60 mbar (0.87 psi))	6
Stainless steel 316L/1.4404 gold-plated, process flange stainless steel 316/1.4408 (not in combination with maximum measuring span 20 mbar (0.29 psi) and 60 mbar (0.87 psi))	8
Material of non-wetted parts	
Die-cast aluminum	1
Stainless steel precision casting CF3M/1.4409 similar to 316L	2
Enclosure	
Dual chamber device	5
Type of protection	
Without Ex	A
Intrinsic safety	B
Flameproof enclosure	C
Flameproof enclosure, intrinsic safety	D
Dust protection by enclosure Zone 21/22 (DIP), increased safety Zone 2	L
Intrinsic safety, dust protection by enclosure Zone 20/21/22 (DIP), increased safety Zone 2	M
Combination of options B, C and L (Zone model)	S
Combination of options B, C and L (Zone model, Class Division)	T
Electrical connections/cable entries	
Thread for cable gland: Cable gland must be ordered separately as option (Axx)	
• 2 × M20 × 1.5	F
• 2 × ½-14 NPT	M
Local operation/display	
Without local display (lid closed)	0
With local display (lid closed)	1
With local display (lid with glass pane)	2

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge pressure (differential pressure series)

Selection and ordering data (continued)

Options	Order code
Add "Z" to article no., add order code and plain text or entry from drop-down list.	
Cable glands included	
Plastic	A00
Metal	A01
Stainless steel	A02
Stainless steel 316L/1.4404	A03
CMP, for XP devices	A10
CAPRI ADE 4F, CuZn, cable inner diameter 7 ... 12 mm, cable outer diameter 10 ... 16 mm	A11
CAPRI ADE 4F, stainless steel, cable inner diameter 7 ... 12 mm, cable outer diameter 10 ... 16 mm	A12
Sealing plug included, plastic	A20
Sealing plug included, metal	A21
Sealing plug included, stainless steel	A22
Sealing plug included, stainless steel 316L/1.4404	A23
Device plug Han mounted left	
Device plug Han 7D (plastic, straight)	A30
Device plug Han 7D (plastic, angled)	A31
Device plug Han 7D (metal, straight)	A32
Device plug Han 7D (metal, angled)	A33
Device plug Han 8D (plastic, straight)	A34
Device plug Han 8D (plastic, angled)	A35
Device plug Han 8D (metal, straight)	A36
Device plug Han 8D (metal, angled)	A37
Cable socket included	
Plastic, for device plug Han 7D and Han 8D	A40
Metal, for device plug Han 7D and Han 8D	A41
Device plug M12 mounted left	
Stainless steel, without cable socket	A62
Stainless steel, with cable socket	A63
Cable entry/device plug mounting	
2 x sealing plugs M20 x 1.5, IP66/68 installed on both sides	A90
2 x sealing plugs 1/2-14 NPT, IP66/68 installed on both sides	A91
Cable gland/device plug mounted left	A97
Cable gland/device plug mounted right	A99
Nameplate labeling (standard labeling: English, unit bar)	
German (bar)	B11
French (bar)	B12
Spanish (bar)	B13
Italian (bar)	B14
Chinese (bar)	B15
Russian (bar)	B16
English (psi)	B20
English (Pa)	B30
Chinese (Pa)	B35
Certificates	
Quality inspection certificate - 5-point factory calibration (IEC 62828-2)	C11
Inspection certificate (EN 10204-3.1) - Material of pressurized and wetted parts	C12
Factory certificate - NACE (MR 0103-2012 and MR 0175-2009)	C13
Factory certificate (EN 10204-2.2) - Wetted parts	C14
Inspection certificate (EN 10204-3.1) - PMI test of pressurized and wetted parts	C15

Selection and ordering data (continued)

Options	Order code
Add "Z" to article no., add order code and plain text or entry from drop-down list.	
Certificates for functional safety	
Functional Safety (IEC 61508) - SIL2/3	C20
Device options	
PDF file with device settings	D10
Double layer coating (epoxy resin and polyurethane) 120 µm of enclosure and lid	D20
FVMQ enclosure sealing	D21
IP66/IP68 degree of protection (not for device plug M12 and Han)	D30
Unlabeled TAG plate	D40
Without labeling of the measuring range on the TAG plate	D41
Stainless steel Ex plate 1.4404/316L	D42
Extension of the medium temperature to -40 °C for measuring cell filling with inert filling liquid Please note step response time T63: 5.5 s (20 and 60 mbar); 1.4 s (250 and 600 mbar); 0.3 s (1.6 and 5 bar)	D52
Overvoltage protection up to 6 kV (internal)	D70
Overvoltage protection up to 6 kV (external)	D71
Labels on transport packaging (provided by customer)	D90
General approval without Ex approval	
Worldwide (CE, UKCA, RCM) except EAC, FM, CSA, KCC	E00
Worldwide (CE, UKCA, RCM, EAC, FM, CSA, KCC)	E01
CSA (USA and Canada)	E06
EAC	E07
FM	E08
KCC	E09
Explosion protection approvals	
ATEX (Europe)	E20
CSA (USA and Canada) ¹⁾	E21
FM (USA and Canada) ¹⁾	E22
IECEx (Worldwide)	E23
EACEx (GOST-R, -K, -B)	E24
INMETRO (Brazil)	E25
KCs (Korea)	E26
NEPSI (China)	E27
PESO (India)	E28
UKR Sepro (Ukraine)	E30
UKEX (United Kingdom)	E33
ATEX (Europe), IECEx (Worldwide) and UKEX (UK)	E47
CSA (Canada) and FM (USA) ¹⁾	E48
ATEX (Europe) and IECEx (Worldwide) + CSA (Canada) and FM (USA) ¹⁾	E49
Marine approvals	
DNV-GL (Det Norske Veritas/Germanischer Lloyd)	E50
LR (Lloyds Register)	E51
BV (Bureau Veritas)	E52
ABS (American Bureau of Shipping)	E53
RMR (Russian Maritime Register)	E55
KR (Korean Register of Shipping)	E56
RINA (Registro Italiano Navale)	E57
CCS (China Classification Society)	E58
Country-specific approvals	
CRN approval Canada (Canadian Registration Number)	E60

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge pressure (differential pressure series)

Selection and ordering data (continued)

Options Add "Z" to article no., add order code and plain text or entry from drop-down list.	Order code
Special approvals	
Oxygen application (with inert liquid, max. 160 bar (2 320 psi) at 100 °C (212 °F))	E80
Dual Seal	E81
WRC/WRAS (drinking water); only with process flange O-rings made of EPDM	E83
NSF61 (drinking water)	E84
ACS (drinking water)	E85
Mounting bracket	
Steel, zinc-plated	H01
Stainless steel 1.4301/304	H02
Stainless steel 1.4404/316L	H03
Process flanges; screw plug with vent valve	
Welded in on right	J08
Welded in on left	J09
Glued in on right	J10
Glued in on left	J11
Flange connections with flange EN 1092-1	
Form B1	
• DN 25 PN 40, stainless steel 1.4571/316Ti	J70
• DN 50 PN 40, stainless steel 1.4571/316Ti	J71
• DN 80 PN 40, stainless steel 1.4571/316Ti	J72
• DN 15 PN 40, stainless steel 1.4571/316Ti	J78
Form C	
• DN 25 PN 40, stainless steel 1.4571/316Ti	J73
• DN 50 PN 40, stainless steel 1.4571/316Ti	J74
• DN 80 PN 40, stainless steel 1.4571/316Ti	J75
Flange connection options	
Flange connection and temperature extension	J76
Flange connection with epoxy resin coating	J77
Process flanges; special materials	
Reserved for 7MF7: without process flanges, without screws, without gaskets	K00
Process flange material alloy C22/2.4602	K01
Process flange material Monel 400/2.4360	K02
Process connection material PVDF, on the side 1/2-14 NPT	K05
Process flanges/process connection material PVDF, flange on the side EN 1092-1 Form B1 DN 25 PN 40, MAWP 4 bar	K06
Process flanges/process connection material PVDF, flange on the side EN 1092-1 Form B1 DN 40 PN 40, MAWP 4 bar	K07
Process flanges; process connection option	
Process flange with process connection G1/2 welded on	K20
Process connection NAM (ASTAVA)	K21
Process flanges chambered with gaskets	
1 x chambered, graphite	K40
1 x chambered, PTFE (FDA-compliant), recommended for gas measurements	K41
Process flanges, gaskets (instead of standard gaskets FKM (FPM))	
O-ring, process flanges, PTFE	K50
O-ring, process flanges, FEP (with silicone core, approved for food)	K51

Selection and ordering data (continued)

Options	Order code
Add "Z" to article no., add order code and plain text or entry from drop-down list.	
O-ring, process flanges, FFKM (FFPM)	K52
O-ring, process flanges, NBR	K53
O-ring, process flanges, EPDM	K54
Process flange options	
Process flanges for vertical differential pressure lines (half process flange)	K81
Process flanges (+) - side front	K82
Process flange screws, process flange nuts, material Monel 400/2.4360	K83
Valve 1/4-18 NPT, material same as process flanges	K84
Valve mounted on the side, measured medium: Gas	K85
Oval flange attached, PTFE seal + fixing screws	K86
Valve manifolds	
With mounted valve manifold (3-way) 7MF9411-5BA, PTFE sealing rings, chrome-plated steel screws and pressure test certified in factory certificate (EN 10204-2.2)	U01
With mounted valve manifold (3-way) 7MF9411-5BA, PTFE sealing rings, stainless steel screws and pressure test certified in factory certificate (EN 10204-2.2)	U02
With mounted valve manifold (5-way) 7MF9411-5CA, PTFE sealing rings, chrome-plated steel screws and pressure test certified in factory certificate (EN 10204-2.2)	U03
With mounted valve manifold (5-way) 7MF9411-5CA, PTFE sealing rings, stainless steel screws and pressure test certified in factory certificate (EN 10204-2.2)	U04
Device settings	
Measuring span: Lower range value (max. 5 characters), upper range value (max. 5 characters), unit [mbar, bar, kPa, MPa, psi, ...], example: -0.5 ... 10.5 psi	Y01
TAG (on stainless steel plate and device parameters, max. 32 characters)	Y15
Measuring point description (on stainless steel plate and device parameters, max. 32 characters)	Y16
TAG short (device parameters, max. 8 characters)	Y17
Local display: [Pressure, Percent], reference [None, Absolute, Gauge], example: Pressure gauge	Y21
Local display: Scaling with standard units [m^3/s , l/s, m, inch, ...]; example 1 ... 5 m	Y22
Local display: Scaling with user-specific units (max. 12 characters), example 1 ... 5 m	Y23
Set PROFIBUS PA device address (1 ... 126)	Y25
Saturation limits instead of 3.8 ... 20.5 mA, example: 3.8 ... 22.0 mA	Y30
Fault current instead of 3.6 mA [22.5 mA, 22.8 mA]	Y31
Damping in seconds instead of 2 s (0.0 ... 100.0 s)	Y32
ID number of special design	Y99

¹⁾ Explosion protection acc. to FM/CSA: suitable for installation according to NEC 500/505.

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge pressure (differential pressure series)

Technical specifications

SITRANS P320 / SITRANS P420 for gauge pressure (differential pressure series)			
Input			
Measured variable	Gauge pressure		
Measuring span (continuously adjustable) or measuring range and max. permissible operating pressure (pursuant to Pressure Equipment Directive 2014/68/EU)	Measuring span	Max. permissible operating pressure MAWP (PS)	Maximum permissible test pressure
	1 ... 20 mbar	160 bar	240 bar
	0.1 ... 2 kPa	16 MPa	24 MPa
	0.4019 ... 8.037 inH ₂ O	2 320 psi	3 481 psi
	1 ... 60 mbar	160 bar	240 bar
	0.1 ... 6 kPa	16 MPa	24 MPa
	0.4019 ... 24.11 inH ₂ O	2 320 psi	3 481 psi
	2.5 ... 250 mbar	160 bar	240 bar
	0.2 ... 25 kPa	16 MPa	24 MPa
	1.005 ... 100.5 inH ₂ O	2 320 psi	3 481 psi
	6 ... 600 mbar	160 bar	240 bar
	0.6 ... 60 kPa	16 MPa	24 MPa
	2.41 ... 241.1 inH ₂ O	2 320 psi	3 481 psi
	16 ... 1 600 mbar	160 bar	240 bar
	1.6 ... 160 kPa	16 MPa	24 MPa
	6.43 ... 643 inH ₂ O	2 320 psi	3 481 psi
	50 ... 5 000 mbar	160 bar	240 bar
	5 ... 500 kPa	16 MPa	24 MPa
	20.09 ... 2 009 inH ₂ O	2 320 psi	3 481 psi
	0.3 ... 30 bar	160 bar	240 bar
	0.03 ... 3 MPa	16 MPa	24 MPa
	4.35 ... 435 psi	2 320 psi	3 481 psi
	8 ... 160 bar	160 bar	240 bar
	0.8 ... 16 MPa	16 MPa	24 MPa
	116 ... 2 320 psi	2 320 psi	3 481 psi
Measuring limits			
• Lower measuring limit			
- Measuring cell with silicone oil filling	30 mbar a/3 kPa a/0.44 psi a		
- Measuring cell with inert oil	30 mbar a/3 kPa a/0.44 psi a		
- Measuring cell with FDA-compliant oil	100 mbar a/10 kPa a/1.45 psi a		
• Upper measuring limit	100% of the max. measuring span (for oxygen measurement max. 100 bar/10 MPa/1450 psi and 60 °C (140 °F) ambient temperature/medium temperature)		
• Lower range value	Between the measuring limits (continuously adjustable)		
Output			
Output signal	HART		
• Lower saturation limit (continuously adjustable)	4 ... 20 mA		
• Upper saturation limit (continuously adjustable)	3.55 mA, factory set to 3.8 mA		
• Ripple (without HART communication)	22.8 mA, factory-set to 20.5 mA or optionally 22.0 mA		
Adjustable damping	I _{pp} ≤ 0.5% of max. output current		
• Current simulator	0 ... 100 s, continuously adjustable over remote operation		
• Failure signal	0 ... 100 s, in increments of 0.1 s, adjustable over display		
Load	3.55 ... 22.8 mA		
• Without HART communication	3.55 ... 22.8 mA		
• With HART communication	Resistance R [Ω] R = (U _H - 10.5 V) / 22.8 mA, U _H : Auxiliary power in V		
Characteristic curve	R = 230 ... 1100 Ω		
Physical bus	• Linearly increasing or linearly decreasing		
Polarity-independent	• Linear increase or decrease or according to the square root (only for differential pressure and flow)		

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for gauge pressure (differential pressure series)

Measuring accuracy

Reference conditions

- According to IEC 62828-1
- Rising characteristic curve
- Lower range value 0 bar/kPa/psi
- Seal diaphragm stainless steel
- Measuring cell with silicone oil filling
- Room temperature 25 °C (77 °F)

Conformity error at limit point setting, including hysteresis and repeatability

Measuring span ratio r (spread, Turn-Down)

- Linear characteristic curve

- 20 mbar/2 kPa/8.031 inH₂O

r = max. measuring span/set measuring span and nominal measuring range

r ≤ 5: ≤ 0.075%

5 < r ≤ 20: ≤ (0.005 · r + 0.05)%

- 60 mbar/6 kPa/24.09 inH₂O

r ≤ 5: ≤ 0.075%

5 < r ≤ 60: ≤ (0.005 · r + 0.05)%

- 250 mbar/25 kPa/3.6 psi

r ≤ 5: ≤ 0.065% (SITRANS P320)

600 mbar/60 kPa/240.9 inH₂O

≤ 0.04% (SITRANS P420)

1 600 mbar/160 kPa/642.4 inH₂O5 000 mbar/500 kPa/2008 inH₂O

30 bar/3 MPa/435 psi

160 bar/16 MPa/2 320 psi

Influence of ambient temperature
in % per 28 °C (50 °F)• 20 mbar/2 kPa/8.031 inH₂O

≤ (0.15 · r + 0.1)%

• 60 mbar/6 kPa/24.09 inH₂O

≤ (0.075 · r + 0.1)%

• 250 mbar/25 kPa/3.6 psi

≤ (0.025 · r + 0.125)% (SITRANS P320)

600 mbar/60 kPa/240.9 inH₂O1 600 mbar/160 kPa/642.4 inH₂O5 000 mbar/500 kPa/2008 inH₂O

30 bar/3 MPa/435 psi

160 bar/16 MPa/2 320 psi

• 250 mbar/25 kPa/3.6 psi

≤ (0.025 · r + 0.0625)% (SITRANS P420)

5 000 mbar/500 kPa/2008 inH₂O• 600 mbar/60 kPa/240.9 inH₂O

≤ (0.0125 · r + 0.0625)% (SITRANS P420)

1 600 mbar/160 kPa/642.4 inH₂O

30 bar/3 MPa/435 psi

160 bar/16 MPa/2 320 psi

Long-term stability at ±30 °C (± 54 °F)

• 20 mbar/2 kPa/8.031 inH₂O

≤ (0.2 · r)% per year

• 60 mbar/6 kPa/24.09 inH₂O

In 5 years ≤ (0.25 · r)%

• 250 mbar/25 kPa/3.6 psi

In 5 years ≤ (0.125 · r)%

600 mbar/60 kPa/240.9 inH₂O

In 10 years ≤ (0.15 · r)%

1 600 mbar/160 kPa/642.4 inH₂O5 000 mbar/500 kPa/2008 inH₂O

30 bar/3 MPa/435 psi

160 bar/16 MPa/2 320 psi

Step response time T₆₃ (without electrical damping)• 20 mbar/2 kPa/8.031 inH₂O

Approx. 0.160 s

• 60 mbar/6 kPa/24.09 inH₂O

Approx. 0.150 s

• 250 mbar/25 kPa/3.6 psi

Approx. 0.135 s

600 mbar/60 kPa/240.9 inH₂O1 600 mbar/160 kPa/642.4 inH₂O5 000 mbar/500 kPa/2008 inH₂O

30 bar/3 MPa/435 psi

160 bar/16 MPa/2 320 psi

Effect of mounting position (in pressure per change of angle)

≤ 0.7 mbar/0.07 kPa/0.010 psi per 10° incline

(zero offset is possible with position error compensation)

Effect of auxiliary power (in % per voltage change)

0.005% per 1 V

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge pressure (differential pressure series)

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for gauge pressure (differential pressure series)

Operating conditions

Medium temperature

- Measuring cell with silicone oil filling -40 ... +100 °C (-40 ... +212 °F)
- Measuring cell 30 bar (435 psi) -20 ... +100 °C (-4 ... +212 °F)
- Measuring cell 160 bar (2 320 psi) -20 ... +100 °C (-4 ... +212 °F)
- Measuring cell with inert oil -20 ... +100 °C (-4 ... +212 °F)

Ambient conditions

- Ambient temperature/enclosure Observe the temperature class in hazardous areas.

- Measuring cell with silicone oil filling -40 ... +85 °C (-40 ... +185 °F)

- Measuring cell with inert oil -40 ... +85 °C (-40 ... +185 °F)

- Display -20 ... +80 °C (-4 ... +176 °F)

- Storage temperature -50 ... +85 °C (-58 ... +185 °F)

- Climatic class in accordance with IEC 60721-3-4 4K4H

Degree of protection

- According to IEC 60529 IP66, IP68

- According to NEMA 250 Type 4X

Electromagnetic compatibility

- Emitted interference and interference immunity According to IEC 61326 and NAMUR NE 21

Structural design

Weight

- Aluminum enclosure: Approx. 3.9 kg (8.5 lbs)
- Stainless steel enclosure: Approx. 5.9 kg (13 lbs)

Material

• Material of wetted parts

- Seal diaphragm Stainless steel, mat. no. 1.4404/316L, Alloy C276, mat. no. 2.4819, Monel, mat. no. 2.4360, tantalum or gold
- Process flanges Stainless steel, mat. no. 1.4408 to PN 160, mat. no. 1.4571/316Ti for PN 420, Alloy C22, 2.4602 or Monel, mat. no. 2.4360

- Sealing plug

1.4404 or as option alloy C22; 2.4602 or Monel mat. no. 2.4360

- O-ring

FPM (Viton) or optionally: PTFE, FEP, FEPM and NBR

• Material of non-wetted parts

- Electronics enclosure

- Low-copper die-cast aluminum GD-AISI 12 or stainless steel precision casting, mat. no. 1.4409/ CF-3M
- Standard: Powder coating with polyurethane
Option: 2 coats: Coat 1: epoxy-based; coat 2: Polyurethane
- Stainless steel nameplate (1.4404/316L)

- Process flange screws

Stainless steel ISO 3506-1 A4-70

- Mounting bracket

Steel, zinc-plated steel, or stainless steel

Process connection

1/4-18 NPT female thread and flange connection with 7/16-20 UNF fastening thread according to EN 61518 or M10 according to DIN 19213 (M12 for PN 420 (MWP 6092 psi))

Electrical connection

Screw terminals

Cable entry via the following screw glands:

- M20 x 1.5
- 1/2-14 NPT
- Device plug Han 7D/Han 8D¹⁾
- Device plug M12

Displays and controls

Buttons

4 buttons for operation directly on the device

Display

- With or without integrated display (optional)
- Lid with inspection window (optional)

Auxiliary power U_H

Terminal voltage on pressure transmitter

10.5 ... 45 V DC
10.5 ... 30 V DC in intrinsically safe mode

Ripple

U_{ss} ≤ 0.2 V (47 ... 125 Hz)

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for gauge pressure (differential pressure series)	
Noise	$U_{eff} \leq 1.2 \text{ mV}$ (0.5 ... 10 kHz)
Auxiliary power	-
Separate supply voltage	-
Certificates and approvals	
Classification according to pressure equipment directive (PED 2014/68/EU)	For gases of fluid group 1 and liquids of fluid group 1; complies with requirements of article 4, paragraph 3 (sound engineering practice)
Drinking water	
• WRAS (England)	No.: 1903094 (option E83)
• ACS (France)	No.: 18 ACC LY 277 (option E85)
• NSF (USA)	No.: 20180920-MH61350 (option E84)
CRN (Canada)	No.: 0F9863.5C (option E60)
Explosion protection acc. to NEPSI (China)	No.: GYJ19.1058X (option E27)
Explosion protection acc. to INMETRO (Brazil)	No.: BRA-18-GE-0035X (option E25)
Explosion protection	
• Intrinsic safety "i"	
- Marking	II 1/2 G Ex ia/ib IIC T4/T6 Ga/Gb
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Connection	To certified intrinsically safe circuits with peak values: $U_i = 30 \text{ V}, I_i = 101 \text{ mA}, P_i = 760 \text{ mW}$ $U_i = 29 \text{ V}, I_i = 110 \text{ mA}, P_i = 800 \text{ mW}$ $L_i = 0.24 \mu\text{H}/C_i = 3.29 \text{ nF}$
- Effective internal inductance/capacitance	
• Flameproof enclosure "d"	Ex II 1/2 G Ex ia/db IIC T4/T6 Ga/Gb
- Marking	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Permissible ambient temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Permissible medium temperature	
- Connection	To a circuit with the operating values: $U_n = 10.5 \dots 45 \text{ V}, 4 \dots 20 \text{ mA}$
• Dust explosion protection for Zones 21, 22	
- Marking	Ex II 2D Ex tb IIIC T120 °C Db
- Permissible ambient temperature	Ex II 3D Ex tc IIIC T120 °C Dc
- Permissible medium temperature	-40 ... +80 °C (-40 ... +176 °F)
- Max. surface temperature	-40 ... +100 °C (-40 ... +212 °F)
- Connection	120 °C (248 °F)
• Dust explosion protection for Zones 20, 21, 22	To a circuit with the operating values: $U_n = 10.5 \dots 45 \text{ V}, 4 \dots 20 \text{ mA}$
- Marking	Ex II 1D Ex ia IIIC T120 °C Da
- Permissible ambient temperature	Ex II 2D Ex ib IIIC T120 °C Db
- Permissible medium temperature	-40 ... +80 °C (-40 ... +176 °F)
- Connection	-40 ... +100 °C (-40 ... +212 °F)
- Effective internal inductance/capacitance	To certified intrinsically safe circuits with peak values: $U_i = 30 \text{ V}, I_i = 101 \text{ mA}, P_i = 760 \text{ mW}$ $U_i = 29 \text{ V}, I_i = 110 \text{ mA}, P_i = 800 \text{ mW}$ $L_i = 0.24 \mu\text{H}/C_i = 3.29 \text{ nF}$
• Type of protection for Zone 2	
- Marking	Ex II 3G Ex ec IIC T4/T6 Gc
- Permissible ambient temperature "ec"	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +40 °C (-40 ... +104 °F) temperature class T6
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- "ec" connection	To a circuit with the operating values: $U_n = 10.5 \dots 30 \text{ V}, 4 \dots 20 \text{ mA}$
• Explosion protection acc. to FM	Available soon

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge pressure (differential pressure series)

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for gauge pressure (differential pressure series)

- Marking (XP/DIP) or IS; NI; S	CL I, DIV 1, GP ABCD T4 ... T6; CL II, DIV 1, GP EFG; CL III; Ex ia IIC T4 ... T6: CL I, DIV 2, GP ABCD T4 ... T6; CL II, DIV 2, GP FG; CL III
• Explosion protection according to CSA	Available soon
- Marking (XP/DIP) or (IS)	CL I, DIV 1, GP ABCD T4 ... T6; CL II, DIV 1, GP EFG; CL III; Ex ia IIC T4 ... T6: CL I, DIV 2, GP ABCD T4 ... T6; CL II, DIV 2, GP FG; CL III
NAMUR recommendations	
• NE 06	Standardized Electrical Signals and Questions Relating to Engineering Technology
• NE 21	Electromagnetic Compatibility (EMC) of Industrial Process and Laboratory Control Equipment
• NE 23	Extra Low Voltage Circuits with Safe Separation
• NE 43	Standardization of the Signal Level for the Failure Information of Digital Transmitters
• NE 53	Software and Hardware of Field Devices and Signal Processing Devices with Digital Electronics
• NE 80	The Application of the Pressure Equipment Directive to Process Control Devices
• NE 105	Specifications for Integrating Fieldbus Devices in Engineering Tools for Field Devices
• NE 107	Self-Monitoring and Diagnosis of Field Devices
• NE 131	NAMUR Standard Device - Field Devices for Standard Applications

¹⁾ Han 8D is identical to Han 8U.

Communication

HART	
HART	230 ... 1 100 Ω
Protocol	HART 7
Software for computer	SIMATIC PDM
PROFIBUS PA	
Simultaneous communication with master class 2 (max.)	4
The address can be set using	Configuration tool or local operation (default setting address 126)
Cyclic data usage	
• Output byte	≤ 35 (7 measured values)
• Input byte	0, 1, or 2 (register operation mode and reset function for dosing)
Internal preprocessing	
Device profile	PROFIBUS PA Profile Version 4.01 Class B. Cyclic data usage compatible with version 3.XX
Number of function blocks	7
• Analog input	Yes, linearly rising or falling characteristic curve
- Adaptation to user-specific process variable	0 ... 100 s
- Electrical damping adjustable	Output/input
- Simulation function	Yes, one upper and lower warning limit and one alarm limit respectively
- Limit monitoring	Can be reset, preset, optional direction of counting, simulation function of register output
• Register (totalizer)	One upper and lower warning limit and one alarm limit respectively
- Limit monitoring	One upper and lower warning limit and one alarm limit respectively
• Physical block	1
Transducer blocks	1
• Pressure transducer block	
- Can be calibrated by applying two pressures	Yes
- Monitoring of sensor limits	Yes
- Specification of a vessel characteristic curve with	Max. 30 nodes
- Square-rooted characteristic curve for flow measurement	Yes
- Tank characteristic curve for volume measurement	Yes

Technical specifications (continued)


Communication	
- Low flow cut-off and implementation point of square-root extraction	Parameterizable
- Simulation function for measured pressure value and sensor temperature	Constant value or by means of parameterizable ramp function
FOUNDATION Fieldbus	
Device profile	FF ITK 6
Function blocks	3 function blocks analog input, 1 function block PID
• Analog input	
- Adaptation to user-specific process variable	Yes, linearly rising or falling characteristic curve
- Electrical damping adjustable	0 ... 100 s
- Simulation function	Output/input (can be locked within the device with a bridge)
- Failure mode	Parameterizable (last good value, substitute value, incorrect value)
- Limit monitoring	Yes, one upper and lower warning limit and one alarm limit respectively
- Square-rooted characteristic curve for flow measurement	Yes
• PID	Standard FOUNDATION Fieldbus function block
• Physical block	1 resource block
Transducer blocks	1 transducer block Pressure with calibration, 1 transducer block LCD
• Pressure transducer block	
- Can be calibrated by applying two pressures	Yes
- Monitoring of sensor limits	Yes
- Simulation function: pressure measurement, sensor temperature and electronics temperature	Constant value or by means of parameterizable ramp function

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge pressure (differential pressure series)

Dimensional drawings



SITRANS P320/P420 pressure transmitter for gauge pressure (differential pressure series), dimensions in mm (inch)

Pressure measurement**Pressure transmitters****for applications with advanced requirements / SITRANS P320/420 / Gauge and absolute pressure, flush-mounted****Selection and ordering data**

	Article No.
Pressure transmitters for gauge and absolute pressure, with flush-mounted diaphragm	
SITRANS P320 for gauge pressure	7MF030
SITRANS P420 for gauge pressure	7MF040
SITRANS P320 for absolute pressure	7MF032
SITRANS P420 for absolute pressure	7MF042
Click the article number for online configuration in the PIA Life Cycle Portal.	
Communication	
HART, 4 ... 20 mA	0
PROFIBUS PA	1
FOUNDATION Fieldbus (FF)	2
Measuring cell filling	
Silicone oil	1
Inert filling liquid	3
Neobee oil	4
Maximum measuring span	
1 000 mbar (14.5 psi)	J
4 000 mbar (58 psi)	N
16 bar (232 psi)	Q
63 bar (914 psi)	T
1 300 mbar a (18.9 psi a)	L
5 000 mbar a (72.5 psi a)	P
30 bar a (435 psi a)	R
Process connection	
Flush-mounted diaphragm	K
Material of wetted parts: Process connection, seal diaphragm	
Stainless steel 316L/1.4404, stainless steel 316L/1.4404	0
Stainless steel 316L/1.4404, alloy C276/2.4819	1
Alloy C22/2.4602, alloy C276/2.4819	2
Material of non-wetted parts	
Die-cast aluminum	1
Stainless steel precision casting CF3M/1.4409 similar to 316L	2
Enclosure	
Dual chamber device	5
Type of protection	
Without Ex	A
Intrinsic safety	B
Flameproof enclosure	C
Flameproof enclosure, intrinsic safety	D
Dust protection by enclosure Zone 21/22 (DIP), increased safety Zone 2	L
Intrinsic safety, dust protection by enclosure Zone 20/21/22 (DIP), increased safety Zone 2	M
Combination of options B, C and L (Zone model)	S
Combination of options B, C and L (Zone model, Class Division)	T
Electrical connections/cable entries	
Thread for cable gland: Cable gland must be ordered separately as option (Axx)	
• 2 x M20 x 1.5	F
• 2 x ½-14 NPT	M
Local operation/display	
Without local display (lid closed)	0
With local display (lid closed)	1
With local display (lid with glass pane)	2
Options	Order code
Add "Z" to article no., add order code and plain text or entry from drop-down list.	
Cable glands included	
Plastic	A00
Metal	A01

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge and absolute pressure, flush-mounted

Selection and ordering data (continued)

Options Add "Z" to article no., add order code and plain text or entry from drop-down list.	Order code
Stainless steel	A02
Stainless steel 316L/1.4404	A03
CMP, for XP devices	A10
CAPRI ADE 4F, CuZn, cable inner diameter 7 ... 12 mm, cable outer diameter 10 ... 16 mm	A11
CAPRI ADE 4F, stainless steel, cable inner diameter 7 ... 12 mm, cable outer diameter 10 ... 16 mm	A12
Sealing plug included, plastic	A20
Sealing plug included, metal	A21
Sealing plug included, stainless steel	A22
Sealing plug included, stainless steel 316L/1.4404	A23
Device plug Han mounted left	
Device plug Han 7D (plastic, straight)	A30
Device plug Han 7D (plastic, angled)	A31
Device plug Han 7D (metal, straight)	A32
Device plug Han 7D (metal, angled)	A33
Device plug Han 8D (plastic, straight)	A34
Device plug Han 8D (plastic, angled)	A35
Device plug Han 8D (metal, straight)	A36
Device plug Han 8D (metal, angled)	A37
Cable socket included	
Plastic, for device plug Han 7D and Han 8D	A40
Metal, for device plug Han 7D and Han 8D	A41
Device plug M12 mounted left	
Stainless steel, without cable socket	A62
Stainless steel, with cable socket	A63
Cable entry/device plug mounting	
2x sealing plugs M20 x 1.5, IP66/68 installed on both sides	A90
2x sealing plugs ½-14 NPT, IP66/68 installed on both sides	A91
Cable gland/device plug mounted left	A97
Cable gland/device plug mounted right	A99
Nameplate labeling (standard labeling: English, unit bar)	
German (bar)	B11
French (bar)	B12
Spanish (bar)	B13
Italian (bar)	B14
Chinese (bar)	B15
Russian (bar)	B16
English (psi)	B20
English (Pa)	B30
Chinese (Pa)	B35
Certificates	
Quality inspection certificate, 5-point factory calibration (IEC 62828-2)	C11
Inspection certificate (EN 10204-3.1) - Material of pressurized and wetted parts	C12
Factory certificate - NACE (MR 0103-2012 and MR 0175-2009)	C13
Factory certificate (EN 10204-2.2) - Wetted parts	C14
Inspection certificate (EN 10204-3.1) - PMI test of pressurized and wetted parts	C15
Certificates for functional safety	
Functional Safety (IEC 61508) - SIL2/3	C20

for applications with advanced requirements / SITRANS P320/420 / Gauge and absolute pressure, flush-mounted

Selection and ordering data (continued)

Options Add "Z" to article no., add order code and plain text or entry from drop-down list.	Order code
Device options	
PDF file with device settings	D10
Double layer coating (epoxy resin and polyurethane) 120 µm of enclosure and lid	D20
FVMQ enclosure sealing	D21
IP66/IP68 degree of protection (not for device plug M12 and Han)	D30
Unlabeled TAG plate	D40
Without labeling of the measuring range on the TAG plate	D41
Stainless steel Ex plate 1.4404/316L	D42
Oversupply protection up to 6 kV (internal)	D70
Oversupply protection up to 6 kV (external)	D71
Labels on transport packaging (provided by customer)	D90
General approval without Ex approval	
Worldwide (CE, UKCA, RCM) except EAC, FM, CSA, KCC	E00
Worldwide (CE, UKCA, RCM, EAC, FM, CSA, KCC)	E01
CSA (USA and Canada)	E06
EAC	E07
FM	E08
KCC	E09
Explosion protection approvals	
ATEX (Europe)	E20
CSA (USA and Canada) ¹⁾	E21
FM (USA and Canada) ¹⁾	E22
IECEx (Worldwide)	E23
EACEx (GOST-R, -K, -B)	E24
INMETRO (Brazil)	E25
KCs (Korea)	E26
NEPSI (China)	E27
PESO (India)	E28
UKR Sepro (Ukraine)	E30
UKEX (United Kingdom)	E33
ATEX (Europe), IECEx (Worldwide) and UKEX (UK)	E47
CSA (Canada) and FM (USA) ¹⁾	E48
ATEX (Europe) and IECEx (Worldwide) + CSA (Canada) and FM (USA) ¹⁾	E49
Marine approvals	
DNV-GL (Det Norske Veritas/Germanischer Lloyd)	E50
LR (Lloyds Register)	E51
BV (Bureau Veritas)	E52
ABS (American Bureau of Shipping)	E53
RMR (Russian Maritime Register)	E55
KR (Korean Register of Shipping)	E56
RINA (Registro Italiano Navale)	E57
CCS (China Classification Society)	E58
Country-specific approvals	
CRN approval Canada (Canadian Registration Number)	E60
Special approvals	
Oxygen application (with inert liquid, max. 160 bar (2 320 psi) at 100 °C (212 °F))	E80
Dual Seal	E81

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge and absolute pressure, flush-mounted

Selection and ordering data (continued)

Options Add "Z" to article no., add order code and plain text or entry from drop-down list.	Order code
WRC/WRAS (drinking water); only with process flange O-rings made of EPDM	E83
NSF61 (drinking water)	E84
ACS (drinking water)	E85
3A (hygiene)	E86
EHEDG (hygiene)	E87
Process flanges, gaskets (instead of standard gaskets FKM (FPM))	
Seal (EN 837-1) material Fe (soft iron)	K60
Seal (EN 837-1) material 1.4571	K61
Seal (EN 837-1) material Cu	K62
Process connection	
Process connection external thread G½, bore hole 11 mm	K80
Flanges according to EN 1092-1 Form B1 and ASME standard B16.5	
EN 1092-1 Form B1	
• DN 50 PN 16	M03
• DN 80 PN 16	M05
• DN 25 PN 40	M10
• DN 40 PN 40	M12
• DN 50 PN 40	M13
• DN 80 PN 40	M15
• DN 40 PN 100	M22
ASME B16.5	
• 1" Class 150 RF	M30
• 1 ½" Class 150 RF	M31
• 2" Class 150 RF	M32
• 3" Class 150 RF	M33
• 4" Class 150 RF	M34
• 1 ½" Class 300 RF	M36
• 2" Class 300 RF	M37
• 3" Class 300 RF	M38
• 4" Class 300 RF	M39
Sanitary connections in accordance with the standard	
Sanitary flange DIN 11851	
• With slotted union nut DN 50 PN 25	N03
• With slotted union nut DN 80 PN 25	N05
Tri-Clamp	
• DIN 32676 DN 50 PN 16	N14
• DIN 32676 DN 65 PN 10	N15
• ISO 2852 2" PN 40	N22
• ISO 2852 3" PN 40	N23
Aseptic screwed connector	
• DIN 11864-1 Form A DN 50 PN 25	N33
• DIN 11864-1 Form A DN 65 PN 25	N34
• DIN 11864-1 Form A DN 80 PN 25	N35
• DIN 11864-1 Form A DN100 PN 25	N36
Aseptic flange with notch	

for applications with advanced requirements / SITRANS P320/420 / Gauge and absolute pressure, flush-mounted

Selection and ordering data (continued)

Options Add "Z" to article no., add order code and plain text or entry from drop-down list.	Order code
• DIN 11864-2 Form A DN 50 PN 16	N43
• DIN 11864-2 Form A DN 65 PN 16	N44
• DIN 11864-2 Form A DN 80 PN 16	N45
• DIN 11864-2 Form A DN100 PN 16	N46
Aseptic clamp with groove	
• DIN 11864-3 Form A DN 50 PN 25	N53
• DIN 11864-3 Form A DN 65 PN 25	N54
• DIN 11864-3 Form A DN 80 PN 16	N55
• DIN 11864-3 Form A DN100 PN 16	N56
Sanitary connections manufacturer-specific	
Varivent type N for pipes DN 40 ... DN 125 PN 40	P06
Sanitary connections special design	
Tank connection	
• TG 52/50 PN 40 with seal	Q00
• TG 52/150 PN 40 with seal	Q01
DRD flange D = 65 mm DN 50 PN 40	Q15
SMS socket	
• With thread 2" PN 25	Q28
• With thread 2 ½" PN 25	Q29
• With thread 3" PN 25	Q30
Weldable sockets for tank connection	
Weldable piece for TG52/50	Q90
Weldable piece for TG52/150	Q91
Connections for the paper industry	
Process connection PMC Style Standard	R00
Process connection PMC Style Minibolt	R01
Weldable sockets for PMC Style Standard	R02
Weldable sockets for PMC Style Minibolt	R03
Threaded connection	
External thread G¾-A DIN 3852-2 Form A	R11
External thread G1-A DIN 3852-2 Form A	R12
External thread G2-A DIN 3852-2 Form A	R14
Special options front-flush	
Temperature decoupler (media temperature up to 200 °C)	R85
Mating connector including seal	R90
Device settings	
Measuring span: Lower range value (max. 5 characters), upper range value (max. 5 characters), unit [mbar, bar, kPa, MPa, psi, ...], example: -0.5 ... 10.5 psi	Y01
TAG (on stainless steel plate and device parameters, max. 32 characters)	Y15
Measuring point description (on stainless steel plate and device parameters, max. 32 characters)	Y16
TAG short (device parameters, max. 8 characters)	Y17
Local display: [Pressure, Percent], reference [None, Absolute, Gauge], example: Pressure gauge	Y21
Local display: Scaling with standard units [m³/s, l/s, m, inch, ...]; example 1 ... 5 m	Y22
Local display: Scaling with user-specific units (max. 12 characters), example 1 ... 5 m	Y23
Set PROFIBUS PA device address (1 ... 126)	Y25

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge and absolute pressure, flush-mounted

Selection and ordering data (continued)

Options	Order code
Add "Z" to article no., add order code and plain text or entry from drop-down list.	
Saturation limits instead of 3.8 ... 20.5 mA, example: 3.8 ... 22.0 mA	Y30
Fault current instead of 3.6 mA [22.5 mA, 22.8 mA]	Y31
Damping in seconds instead of 2 s (0.0 ... 100.0 s)	Y32
ID number of special design	Y99

¹⁾ Explosion protection acc. to FM/CSA: suitable for installation according to NEC 500/505.

Technical specifications

SITRANS P320 / SITRANS P420 for gauge and absolute pressure, with flush-mounted diaphragm			
Input of gauge pressure with front-flush diaphragm			
Measured variable	Gauge pressure		
Measuring span (continuously adjustable) or measuring range, max. permissible operating pressure and max. permissible test pressure	Measuring span 0.01 ... 1 bar 1 ... 100 kPa 0.15 ... 14.5 psi 0.04 ... 4 bar 4 ... 400 kPa 0.58 ... 58 psi 0.16 ... 16 bar 0.016 ... 1.6 MPa 2.3 ... 232 psi 0.6 ... 63 bar 0.063 ... 6.3 MPa 9.1 ... 914 psi	Max. permissible operating pressure MAWP (PS) Refer to the information on the nameplate of the pressure transmitter and the data on the mounting flange ¹⁾	Maximum permissible test pressure
Measuring limits			
• Lower measuring limit			
- Measuring cell with silicone oil filling	100 mbar a/10 kPa a/1.45 psi a		
- Measuring cell with inert oil	100 mbar a/10 kPa a/1.45 psi a		
- Measuring cell with FDA-compliant oil	100 mbar a/10 kPa a/1.45 psi a		
• Upper measuring limit	100% of max. measuring span		
Input of absolute pressure, with flush-mounted diaphragm			
Measured variable	Absolute pressure		
Measuring span (continuously adjustable) or measuring range, max. permissible operating pressure and max. permissible test pressure	Measuring span 43 ... 1300 mbar a 4.3 ... 130 kPa a 17 ... 525 inH ₂ O a 166 ... 5 000 mbar a 16.6 ... 500 kPa a 2.41 ... 72.5 psi a 1 ... 30 bar a 0.1 ... 3 MPa a 14.5 ... 435 psi a	Max. permissible operating pressure MAWP (PS) Refer to the information on the nameplate of the pressure transmitter and the data on the mounting flange ¹⁾	Maximum permissible test pressure
Measuring limits		Depending on the process connection, the measuring span may differ from these values.	
• Lower measuring limit			
- Measuring cell with silicone oil filling	0 bar a/0 kPa a/0 psi a		
• Upper measuring limit	100% of max. measuring span		
Lower range value	Between the measuring limits (continuously adjustable)		

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for gauge and absolute pressure, with flush-mounted diaphragm	
Output	HART
Output signal	4 ... 20 mA
• Lower saturation limit (continuously adjustable)	3.55 mA, factory set to 3.8 mA
• Upper saturation limit (continuously adjustable)	22.8 mA, factory-set to 20.5 mA or optionally 22.0 mA
• Ripple (without HART communication)	$I_{pp} \leq 0.5\%$ of max. output current
Adjustable damping	0 ... 100 s, continuously adjustable over remote operation 0 ... 100 s, in increments of 0.1 s, adjustable over local display
• Current simulator	3.55 ... 22.8 mA
• Failure signal	3.55 ... 22.8 mA
Load	Resistance R [Ω]
• Without HART communication	$R = (U_H - 10.5 \text{ V}) / 22.8 \text{ mA}$, U_H : Auxiliary power in V
• With HART communication	$R = 230 \dots 1100 \Omega$
Characteristic curve	• Linearly increasing or linearly decreasing • Linear increase or decrease or according to the square root (only for differential pressure and flow)
Physical bus	-
Polarity-independent	-
Gauge pressure measuring accuracy, with front-flush diaphragm	
Reference conditions	<ul style="list-style-type: none"> According to IEC 62828-1 Rising characteristic curve Lower range value 0 bar/kPa/psi Seal diaphragm stainless steel Measuring cell with silicone oil filling Room temperature 25 °C (77 °F)
Characteristic curve deviation at limit point setting, including hysteresis and repeatability	
Measuring span ratio r (spread, Turn-Down)	$r = \text{maximum measuring span}/\text{set measuring span or nominal measuring range}$
• Linear characteristic curve	
- 1 bar/100 kPa/14.5 psi 4 bar/400 kPa/58 psi 16 bar/1.6 MPa/232 psi 63 bar/6.3 MPa/914 psi	$r \leq 5:$ $\leq 0.075\%$ $5 < r \leq 100:$ $\leq (0.005 \cdot r + 0.05)\%$
Influence of ambient temperature in % per 28 °C (50 °F)	
• 1 bar/100 kPa/14.5 psi 4 bar/400 kPa/58 psi 16 bar/1.6 MPa/232 psi 63 bar/6.3 MPa/914 psi	$\leq (0.08 \cdot r + 0.16)\%$
Influence of the medium temperature (in pressure per temperature unit)	
• Temperature difference between medium temperature and ambient temperature	3 mbar/0.3 kPa/0.04 psi per 10 K
Long-term stability at ±30 °C (± 54 °F)	
• 1 bar/100 kPa/14.5 psi 4 bar/400 kPa/58 psi	In 5 years $\leq (0.25 \cdot r)\%$
• 16 bar/1.6 MPa/232 psi 63 bar/6.3 MPa/914 psi	In 5 years $\leq (0.125 \cdot r)\%$
Step response time T_{63} (without electrical damping)	$\leq 0.105 \text{ s}$
Effect of mounting position (in pressure per change of angle)	0.4 mbar/0.04 kPa/0.006 per 10° incline (zero offset is possible with position error compensation)
Effect of auxiliary power (in % per voltage change)	0.005% per 1 V

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge and absolute pressure, flush-mounted

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for gauge and absolute pressure, with flush-mounted diaphragm

Absolute pressure measuring accuracy with flush diaphragm

Reference conditions

- According to IEC 62828-1
- Rising characteristic curve
- Lower range value 0 bar/kPa/psi
- Seal diaphragm stainless steel
- Measuring cell with silicone oil filling
- Room temperature 25 °C (77 °F)

Characteristic curve deviation at limit point setting, including hysteresis and repeatability

Measuring span ratio r (spread, Turn-Down)

- Linear characteristic curve
- All measuring cells

r = maximum measuring span/set measuring span or nominal measuring range

$r \leq 10:$	$\leq 0.2\%$
$10 < r \leq 30:$	$\leq 0.4\%$

Influence of ambient temperature in % per 28 °C (50 °F)

- All measuring cells

$\leq (0.16 \cdot r + 0.24)\%$

Influence of the medium temperature (in pressure per temperature unit)

- Temperature difference between medium temperature and ambient temperature

3 mbar/0.3 kPa/0.04 psi per 10 K

Long-term stability at $\pm 30^{\circ}\text{C}$ ($\pm 54^{\circ}\text{F}$)

- All measuring cells

In 5 years $\leq (0.25 \cdot r)\%$

Step response time T_{63} (without electrical damping)

≤ 0.105 s

Effect of mounting position (in pressure per change of angle)

0.4 mbar/0.04 kPa/0.006 per 10° incline
(zero offset is possible with position error compensation)

Effect of auxiliary power (in % per voltage change)

0.005% per 1 V

Operating conditions

Medium temperature²⁾

- Measuring cell with silicone oil filling
- Measuring cell with inert oil
- Measuring cell with FDA-compliant oil

-40 ... +150 °C (-40 ... +302 °F)
-40 ... +200 °C (-40 ... +392 °F) with temperature decoupler
-20 ... +100 °C (-4 ... +212 °F)
-10 ... +150 °C (14 ... 302 °F)

Ambient conditions

- Ambient temperature/enclosure

Observe the temperature class in hazardous areas.

- Measuring cell with silicone oil filling

-40 ... +85 °C (-40 ... +185 °F)

- Measuring cell with inert fill oil (different pressure classes)

1 bar/100 kPa/14.5 psi -40 ... +85 °C (-40 ... +185 °F)
4 bar/400 kPa/58 psi
16 bar/1.6 MPa/232 psi
63 bar/6.3 MPa/914 psi

- Measuring cell with FDA-compliant oil

-10 ... +85 °C (14 ... +185 °F)

- Local display

-20 ... +80 °C (-4 ... +176 °F)

- Storage temperature

-50 ... +85 °C (-58 ... +185 °F) (with FDA-compliant oil: -20 ... +85 °C (-4 ... +185 °F))

- Climatic class in accordance with IEC 60721-3-4

4K4H

- Type of protection

IP66, IP68

- According to IEC 60529

Type 4X

- According to NEMA 250

- Electromagnetic compatibility

- Emitted interference and interference immunity

According to IEC 61326 and NAMUR NE 21

Structural design

Weight

Pressure transmitter without mounting flange

- Aluminum enclosure: Approx. 1.8 kg (3.9 lb)
- Stainless steel enclosure: Approx. 3.8 kg (8.3 lb)

Material

for applications with advanced requirements / SITRANS P320/420 / Gauge and absolute pressure, flush-mounted

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for gauge and absolute pressure, with flush-mounted diaphragm	
• Material of wetted parts	
- Process connection	Stainless steel, mat. no. 1.4404/316L
- Seal diaphragm	Stainless steel, material no. 1.4404/316L or Alloy C276, material no. 2.4819
• Material of non-wetted parts	
- Electronics enclosure	<ul style="list-style-type: none"> • Low-copper die-cast aluminum GD-AlSi 12 or stainless steel precision casting, mat. no. 1.4409/ CF-3M • Standard: Powder coating with polyurethane Option: 2 coats: Coat 1: Epoxy-based; coat 2: Polyurethane • Stainless steel nameplate (1.4404/316L)
- Mounting bracket	Steel, zinc-plated steel, or stainless steel
Process connection	<ul style="list-style-type: none"> • Flanges according to EN and ASME • F&B and pharmaceutical flanges • BioConnect/BioControl • PMC style
Electrical connection	<p>Cable entry via the following screw glands:</p> <ul style="list-style-type: none"> • M20 x 1.5 • ½-14 NPT • Device plug Han 7D/Han 8D³⁾ • Device plug M12
Displays and controls	
Buttons	4 buttons for operation directly on the device
Local display	<ul style="list-style-type: none"> • With or without integrated local display (optional) • Lid with inspection window (optional)
Auxiliary power U _H	
Terminal voltage on pressure transmitter	10.5 ... 45 V DC 10.5 ... 30 V DC in intrinsically safe mode
Ripple	U _{SS} ≤ 0.2 V (47 ... 125 Hz)
Noise	U _{eff} ≤ 1.2 mV (0.5 ... 10 kHz)
Auxiliary power	–
Separate supply voltage	–
Certificates and approvals	
Classification according to pressure equipment directive (PED 2014/68/EU)	For gases of fluid group 1 and liquids of fluid group 1; complies with requirements of article 4, paragraph 3 (sound engineering practice)
Drinking water	
• WRAS (England)	No.: 1903094 (option E83)
• ACS (France)	No.: 18 ACC LY 277 (option E85)
• NSF (USA)	No.: 20180920-MH61350 (option E84)
CRN (Canada)	No.: 0F9863.5C (option E60)
Explosion protection acc. to NEPSI (China)	No.: GYJ19.1058X (option E27)
Explosion protection acc. to INMETRO (Brazil)	No.: BRA-18-GE-0035X (option E25)
Explosion protection	
• Intrinsic safety "i"	
- Marking	II 1/2 G Ex ia(ib) IIC T4/T6 Ga/Gb
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Connection	To certified intrinsically safe circuits with peak values: U _i = 30 V, I _i = 101 mA, P _i = 760 mW U _i = 29 V, I _i = 110 mA, P _i = 800 mW L _i = 0.24 µH/C _i = 3.29 nF
- Effective internal inductance/capacitance	
• Flameproof enclosure "d"	
- Marking	Ex II 1/2 G Ex ia/db IIC T4/T6 Ga/Gb

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge and absolute pressure, flush-mounted

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for gauge and absolute pressure, with flush-mounted diaphragm

- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F) temperature class T4
- Permissible medium temperature	-40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Connection	To a circuit with the operating values: $U_n = 10.5 \dots 45 \text{ V}$, $4 \dots 20 \text{ mA}$
• Dust explosion protection for Zones 21, 22	
- Marking	Ex II 2D Ex tb IIIC T120 °C Db Ex II 3D Ex tc IIIC T120 °C Dc
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F)
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F)
- Max. surface temperature	120 °C (248 °F)
- Connection	To a circuit with the operating values: $U_n = 10.5 \dots 45 \text{ V}$, $4 \dots 20 \text{ mA}$
• Dust explosion protection for Zones 20, 21, 22	
- Marking	Ex II 1D Ex ia IIIC T120 °C Da Ex II 2D Ex ib IIIC T120 °C Db
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F)
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F)
- Connection	To certified intrinsically safe circuits with peak values: $U_i = 30 \text{ V}$, $I_i = 101 \text{ mA}$, $P_i = 760 \text{ mW}$ $U_i = 29 \text{ V}$, $I_i = 110 \text{ mA}$, $P_i = 800 \text{ mW}$ $L_i = 0.24 \mu\text{H}/C_i = 3.29 \text{ nF}$
- Effective internal inductance/capacitance	
• Type of protection (Ex) for zone 2	
- Marking	Ex II 3G Ex ec IIC T4/T6 Gc
- Permissible ambient temperature "ec"	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +40 °C (-40 ... +104 °F) temperature class T6
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- "ec" connection	To a circuit with the operating values: $U_n = 10.5 \dots 30 \text{ V}$, $4 \dots 20 \text{ mA}$
• Explosion protection acc. to FM	Available soon
- Marking (XP/DIP) or IS; NI; S	CL I, DIV 1, GP ABCD T4 ... T6; CL II, DIV 1, GP EFG; CL III; Ex ia IIC T4 ... T6: CL I, DIV 2, GP ABCD T4 ... T6; CL II, DIV 2, GP FG; CL III
• Explosion protection according to CSA	Available soon
- Marking (XP/DIP) or (IS)	CL I, DIV 1, GP ABCD T4 ... T6; CL II, DIV 1, GP EFG; CL III; Ex ia IIC T4 ... T6: CL I, DIV 2, GP ABCD T4 ... T6; CL II, DIV 2, GP FG; CL III
NAMUR recommendations	
• NE 06	Standardized Electrical Signals and Questions Relating to Engineering Technology
• NE 21	Electromagnetic Compatibility (EMC) of Industrial Process and Laboratory Control Equipment
• NE 23	Extra Low Voltage Circuits with Safe Separation
• NE 43	Standardization of the Signal Level for the Failure Information of Digital Transmitters with analog output signal
• NE 53	Software and Hardware of Field Devices and Signal Processing Devices with Digital Electronics
• NE 80	The Application of the Pressure Equipment Directive to Process Control Devices
• NE 105	Specifications for Integrating Fieldbus Devices in Engineering Tools for Field Devices
• NE 107	Self-Monitoring and Diagnosis of Field Devices
• NE 131	NAMUR Standard Device - Field Devices for Standard Applications

¹⁾ The MAWP value of the pressure transmitter can be lower than the PN value of the mounting flange and vice versa.

To determine the maximum permissible operating pressure and the maximum permissible test pressure, use the lowest value as reference.

²⁾ Observe the temperature limits in the process connection standards (e.g. DIN 32676 and DIN 11851) for the maximum medium temperature for flush-mounted process connections.

³⁾ Han 8D is identical to Han 8U.

Communication

HART

HART

230 ... 1 100 Ω

Protocol

HART 7

Software for computer

SIMATIC PDM

Technical specifications (continued)

Communication	
PROFIBUS PA	
Simultaneous communication with master class 2 (max.)	4
The address can be set using	Configuration tool or local operation (default setting address 126)
Cyclic data usage	≤ 35 (7 measured values)
• Output byte	
• Input byte	0, 1, or 2 (register operation mode and reset function for dosing)
Internal preprocessing	
Device profile	PROFIBUS PA Profile Version 4.01 Class B. Cyclic data usage compatible with version 3.XX
Number of function blocks	7
• Analog input	
- Adaptation to user-specific process variable	Yes, linearly rising or falling characteristic curve
- Electrical damping adjustable	0 ... 100 s
- Simulation function	Output/input
- Limit monitoring	Yes, one upper and lower warning limit and one alarm limit respectively
• Register (totalizer)	Can be reset, preset, optional direction of counting, simulation function of register output
- Limit monitoring	One upper and lower warning limit and one alarm limit respectively
• Physical block	1
Transducer blocks	1
• Pressure transducer block	
- Can be calibrated by applying two pressures	Yes
- Monitoring of sensor limits	Yes
- Specification of a vessel characteristic curve with	Max. 30 nodes
- Square-rooted characteristic curve for flow measurement	Yes
- Tank characteristic curve for volume measurement	Yes
- Low flow cut-off and implementation point of square-root extraction	Parameterizable
- Simulation function for measured pressure value and sensor temperature	Constant value or by means of parameterizable ramp function
FOUNDATION Fieldbus	
Device profile	FF ITK 6
Function blocks	3 function blocks analog input, 1 function block PID
• Analog input	
- Adaptation to user-specific process variable	Yes, linearly rising or falling characteristic curve
- Electrical damping adjustable	0 ... 100 s
- Simulation function	Output/input (can be locked within the device with a bridge)
- Failure mode	Parameterizable (last good value, substitute value, incorrect value)
- Limit monitoring	Yes, one upper and lower warning limit and one alarm limit respectively
- Square-rooted characteristic curve for flow measurement	Yes
• PID	Standard FOUNDATION Fieldbus function block
• Physical block	1 resource block

Pressure measurement

Pressure transmitters


for applications with advanced requirements / SITRANS P320/420 / Gauge and absolute pressure, flush-mounted

Technical specifications (continued)

Communication

Transducer blocks	1 transducer block Pressure with calibration, 1 transducer block LCD
• Pressure transducer block	
- Can be calibrated by applying two pressures	Yes
- Monitoring of sensor limits	Yes
- Simulation function: pressure measurement, sensor temperature and electronics temperature	Constant value or by means of parameterizable ramp function

Dimensional drawings



SITRANS P320/P420 pressure transmitter, with flush-mounted diaphragm, dimensions in mm (inch)

This figure consists of a SITRANS P320/P420 with an example flange.
In this figure, the height is divided into H₁ and H₂.

H₁ = Height of the SITRANS P320/P420 up to a defined cross-section

H₂ = Height of the flange up to this defined cross-section

Only the height H₂ is indicated in the dimensions of the flanges.

for applications with advanced requirements / SITRANS P320/420 / Gauge and absolute pressure, flush-mounted

Dimensional drawings (continued)**Flanges according to EN and ASME**

Flange	Order code	DN	PN	$\varnothing D$	H_2
EN 1092-1					
	M03	50	16	165 mm (6.5 inches)	Approx. 52 mm
	M05	80	16	200 mm (7.9 inches)	(2 inches)
	M10	25	40	115 mm (4.5 inches)	
	M12	40	40	150 mm (5.9 inches)	
	M13	50	40	165 mm (6.5 inches)	
	M15	80	40	200 mm (7.9 inches)	
	M22	40	100	170 mm (6.7 inches)	
ASME B16.5					
	M30	1 inch	150	110 mm (4.3 inches)	Approx. 52 mm
	M31	1½ inches	150	125 mm (4.9 inches)	(2 inches)
	M32	2 inches	150	150 mm (5.9 inches)	
	M33	3 inches	150	190 mm (7.5 inches)	
	M34	4 inches	150	230 mm (9.1 inches)	
	M36	1½ inches	300	155 mm (6.1 inches)	
	M37	2 inches	300	165 mm (6.5 inches)	
	M38	3 inches	300	210 mm (8.1 inches)	
	M39	4 inches	300	255 mm (10.0 inches)	

NuG and pharmaceutical connectionsConnections according to DIN

Connection	Order code	DN	PN	$\varnothing D$	H_2
DIN 11851 (dairy connection with slotted union nut)					
	N03	50	25	92 mm (3.6 inches)	Approx. 52 mm
	N05	80	25	127 mm (5.0 inches)	(2 inches)
Tri-Clamp acc. to DIN 32676					
	N14	50	16	64 mm (2.5 inches)	Approx. 52 mm
	N15	65	16	91 mm (3.6 inches)	(2 inches)
	N22	2 inches	16	64 mm (2.5 inches)	
	N23	3 inches	10	91 mm (3.6 inches)	







Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Gauge and absolute pressure, flush-mounted

Dimensional drawings (continued)

Other connections

Connection	Order code	DN	PN	$\varnothing D$	H_2
Varivent connection 	P06	40 ... 125	40	84 mm (3.3 inches)	Approx. 52 mm (2 inches)
Sanitary process connection according to DRD 	Q15	65	40	105 mm (4.1 inches)	Approx. 52 mm (2 inches)
Threaded connection G$\frac{3}{4}$", G1" and G2" according to DIN 3852-2 form A 	R11 R12 R14	$\frac{3}{4}$ inch 1 inch 2 inches	60 60 60	37 mm (1.5 inches) 48 mm (1.9 inches) 78 mm (3.1 inches)	Approx. 45 mm (1.8 inches) Approx. 47 mm (1.9 inches) Approx. 52 mm (2 inches)
Tank connection TG 52/50 and TG52/150 	Q00 Q01	25	40	63 mm (2.5 inches)	Approx. 63 mm (2.5 inches)
SMS screwed connector 	Q28 Q29 Q30	2 inches 2½ inches 3 inches	25 25 25	70 x 1/6 mm 85 x 1/6 mm 98 x 1/6 mm	Approx. 52 mm (2.1 inches)
Aseptic screwed connector according to DIN 11864-1 Form A 	N33 N34 N35 N36	50 65 80 100	25 25 25 25	78 x 1/6 inch 95 x 1/6 inch 110 x ¼ inch 130 x ¼ inch	Approx. 52 mm (2.1 inches)

for applications with advanced requirements / SITRANS P320/420 / Gauge and absolute pressure, flush-mounted

Dimensional drawings (continued)

Connection	Order code	DN	PN	$\varnothing D$	H_2
Aseptic flange with notch according to DIN 11864-2 Form A	N43 N44 N45 N46	50 65 80 100	16 16 16 16	94 (3.7 inches) 113 (4.4 inches) 133 (5.2 inches) 159 (6.3 inches)	Approx. 52 mm (2.1 inches)
Aseptic clamp with groove according to DIN 11864-3 Form A	N53 N54 N55 N56	50 65 80 100	25 25 16 16	77.5 (3.1 inch) 91 (3.6 inch) 106 (4.2 inches) 130 (5.1 inches)	Approx. 52 mm (2.1 inches)
Process connection PMC Style Standard	R00	-	-	40.9 mm (1.6 inches)	Approx. 36.8 mm (1.4 inches)
Process connection PMC Style Minibolt	R01	-	-	26.3 mm (1.0 inch)	Approx. 33.1 mm (1.3 inches)

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Absolute pressure (pressure series)

Selection and ordering data

	Article No.
Pressure transmitters for absolute pressure (pressure series)	
SITRANS P320	7MF032
SITRANS P420	7MF042
Click the article number for online configuration in the PIA Life Cycle Portal.	
Communication	
HART, 4 ... 20 mA	0
PROFIBUS PA	1
FOUNDATION Fieldbus (FF)	2
Measuring cell filling	
Silicone oil	1
Inert filling liquid	3
Maximum measuring span	
250 mbar a (100.5 inH ₂ O a)	F
1 300 mbar a (522 inH ₂ O a)	L
5 000 mbar a (72.5 psi a)	P
30 bar a (435 psi a)	R
160 bar a (2 321 psi a)	V
400 bar a (5 802 psi a)	W
700 bar a (10 153 psi a)	X
Process connection	
External thread M20 × 1.5	B
External thread G½ (EN 837-1)	D
Internal thread ½-14 NPT	E
External thread ½-14 NPT	F
Oval flange, fastening thread: 7/16-20 UNF (IEC 61518)	G
Oval flange, fastening thread: M10 (DIN 19213)	H
Oval flange, fastening thread: M12 (DIN 19213)	J
Version for diaphragm seal pressure	U
Material of wetted parts: Process connection, seal diaphragm	
Stainless steel 316L/1.4404, stainless steel 316L/1.4404	0
Stainless steel 16L/1.4404, alloy C276/2.4819	1
Alloy C22/2.4602, alloy C276/2.4819	2
Stainless steel 316L/1.4404, stainless steel 316L/1.4404 gold-plated	7
Material of non-wetted parts	
Die-cast aluminum	1
Stainless steel precision casting CF3M/1.4409 similar to 316L	2
Enclosure	5
Dual chamber device	
Type of protection	
Without Ex	A
Intrinsic safety	B
Flameproof enclosure	C
Flameproof enclosure, intrinsic safety	D
Dust protection by enclosure Zone 21/22 (DIP), increased safety Zone 2	L
Intrinsic safety, dust protection by enclosure Zone 20/21/22 (DIP), increased safety Zone 2	M
Combination of options B, C and L (Zone model)	S
Combination of options B, C and L (Zone model, Class Division)	T
Electrical connections/cable entries	
Thread for cable gland: Cable gland must be ordered separately as option (Axx)	
• 2 × M20 × 1.5	F
• 2 × ½-14 NPT	M
Local operation/display	
Without local display (lid closed)	0
With local display (lid closed)	1
With local display (lid with glass pane)	2

Selection and ordering data (continued)

Options Add "Z" to article number, specify order code and plain text or entry from drop-down list.	Order code
Cable glands included	
Plastic	A00
Metal	A01
Stainless steel	A02
Stainless steel 316L/1.4404	A03
CMP, for XP devices	A10
CAPRI ADE 4F, CuZn, cable inner diameter 7 ... 12 mm, cable outer diameter 10 ... 16 mm	A11
CAPRI ADE 4F, stainless steel, cable inner diameter 7 ... 12 mm, cable outer diameter 10 ... 16 mm	A12
Sealing plug included, plastic	A20
Sealing plug included, metal	A21
Sealing plug included, stainless steel	A22
Sealing plug included, stainless steel 316L/1.4404	A23
Device plug Han mounted left	
Device plug Han 7D (plastic, straight)	A30
Device plug Han 7D (plastic, angled)	A31
Device plug Han 7D (metal, straight)	A32
Device plug Han 7D (metal, angled)	A33
Device plug Han 8D (plastic, straight)	A34
Device plug Han 8D (plastic, angled)	A35
Device plug Han 8D (metal, straight)	A36
Device plug Han 8D (metal, angled)	A37
Cable socket included	
Plastic, for device plug Han 7D and Han 8D	A40
Metal, for device plug Han 7D and Han 8D	A41
Device plug M12 mounted left	
Stainless steel, without cable socket	A62
Stainless steel, with cable socket	A63
Cable entry/device plug mounting	
2x sealing plugs M20 x 1.5, IP66/68 installed on both sides	A90
2x sealing plugs ½-14 NPT, IP66/68 installed on both sides	A91
Cable gland/device plug mounted left	A97
Cable gland/device plug mounted right	A99
Nameplate labeling (standard labeling: English, unit bar)	
German (bar)	B11
French (bar)	B12
Spanish (bar)	B13
Italian (bar)	B14
Chinese (bar)	B15
Russian (bar)	B16
English (psi)	B20
English (Pa)	B30
Chinese (Pa)	B35
Certificates	
Quality inspection certificate, 5-point factory calibration (IEC 62828-2)	C11
Inspection certificate (EN 10204-3.1) - Material of pressurized and wetted parts	C12
Factory certificate - NACE (MR 0103-2012 and MR 0175-2009)	C13
Factory certificate (EN 10204-2.2) - Wetted parts	C14
Inspection certificate (EN 10204-3.1) - PMI test of pressurized and wetted parts	C15

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Absolute pressure (pressure series)

Selection and ordering data (continued)

Options	Order code
Add "Z" to article number, specify order code and plain text or entry from drop-down list.	
Certificates for functional safety	
Functional Safety (IEC 61508) - SIL2/3	C20
Device options	
PDF file with device settings	D10
Double layer coating (epoxy resin and polyurethane) 120 µm of enclosure and lid	D20
FVMQ enclosure sealing	D21
IP66/IP68 degree of protection (not for device plug M12 and Han)	D30
Unlabeled TAG plate	D40
Without labeling of the measuring range on the TAG plate	D41
Stainless steel Ex plate 1.4404/316L	D42
Oversupply protection up to 6 kV (internal)	D70
Oversupply protection up to 6 kV (external)	D71
Labels on transport packaging (provided by customer)	D90
General approval without Ex approval	
Worldwide (CE, UKCA, RCM) except EAC, FM, CSA, KCC	E00
Worldwide (CE, UKCA, RCM, EAC, FM, CSA, KCC)	E01
CSA (USA and Canada)	E06
EAC	E07
FM	E08
KCC	E09
Explosion protection approvals	
ATEX (Europe)	E20
CSA (USA and Canada) ¹⁾	E21
FM (USA and Canada) ¹⁾	E22
IECEx (Worldwide)	E23
EACEx (GOST-R, -K, -B)	E24
INMETRO (Brazil)	E25
KCs (Korea)	E26
NEPSI (China)	E27
PESO (India)	E28
UKR Sepro (Ukraine)	E30
UKEX (United Kingdom)	E33
ATEX (Europe), IECEx (Worldwide) and UKEX (UK)	E47
CSA (Canada) and FM (USA) ¹⁾	E48
ATEX (Europe) and IECEx (Worldwide) + CSA (Canada) and FM (USA) ¹⁾	E49
Marine approvals	
DNV-GL (Det Norske Veritas/Germanischer Lloyd)	E50
LR (Lloyds Register)	E51
BV (Bureau Veritas)	E52
ABS (American Bureau of Shipping)	E53
RMR (Russian Maritime Register)	E55
KR (Korean Register of Shipping)	E56
RINA (Registro Italiano Navale)	E57
CCS (China Classification Society)	E58
Country-specific approvals	
CRN approval Canada (Canadian Registration Number)	E60
Special approvals	
Oxygen application (with inert liquid, max. 160 bar (2 320 psi) at 100 °C (212 °F))	E80
Dual Seal	E81

Selection and ordering data (continued)

Options Add "Z" to article number, specify order code and plain text or entry from drop-down list.	Order code
WRC/WRAS (drinking water); only with process flange O-rings made of EPDM	E83
NSF61 (drinking water)	E84
ACS (drinking water)	E85
Mounting bracket	
Steel, zinc-plated	H01
Stainless steel 1.4301/304	H02
Stainless steel 1.4404/316L	H03
Flange connections with flange EN 1092-1	
With flange adapter G½ Form B1	
• DN 25 PN 40, stainless steel 1.4571/316Ti	J80
• DN 50 PN 40, stainless steel 1.4571/316Ti	J81
• DN 80 PN 40, stainless steel 1.4571/316Ti	J82
With water trap G½ form B1	
• DN 25 PN 40, stainless steel 1.4571/316Ti	J83
• DN 50 PN 40, stainless steel 1.4571/316Ti	J84
• DN 80 PN 40, stainless steel 1.4571/316Ti	J85
• DN 25 PN 100, stainless steel 1.4571/316Ti	J86
Process flanges, gaskets (instead of standard gaskets FKM (FPM))	
Gasket (EN 837-1) material Fe (soft iron)	K60
Gasket (EN 837-1) material 1.4571	K61
Gasket (EN 837-1) material Cu	K62
Process connection	
Process connection external thread G½, bore hole 11 mm	K80
Shut-off valves, valve manifolds	
With mounted valve manifold 7MF9011-4EA, process connection at transmitter G½ shank, PTFE sealing ring and pressure test certified in factory certificate (EN 10204-2.2)	T02
With mounted valve manifold 7MF9011-4FA, process connection at transmitter internal thread ½-14 NPT, sealing tape. With PTFE sealing ring and pressure test certified in factory certificate (EN 10204-2.2)	T03
With mounted valve manifold 7MF9411-5AA, process connection at transmitter oval flange with PTFE sealing ring, steel fixing screws, pressure test certified in factory certificate (EN 10204-2.2)	T05
With mounted valve manifold 7MF9411-5AA, process connection at transmitter oval flange with PTFE sealing ring, stainless steel fixing screws, pressure test certified in factory certificate (EN 10204-2.2)	T06
Device settings	
Measuring span: Lower range value (max. 5 characters), upper range value (max. 5 characters), unit [mbar, bar, kPa, MPa, psi, ...], example: -0.5 ... 10.5 psi	Y01
TAG (on stainless steel plate and device parameters, max. 32 characters)	Y15
Measuring point description (on stainless steel plate and device parameters, max. 32 characters)	Y16
TAG short (device parameters, max. 8 characters)	Y17
Local display: [Pressure, Percent], reference [None, Absolute, Gauge], example: Pressure gauge	Y21
Local display: Scaling with standard units [m^3/s , l/s , m, inch, ...]; example 1 ... 5 m	Y22
Local display: Scaling with user-specific units (max. 12 characters), example 1 ... 5 m	Y23
Set PROFIBUS PA device address (1 ... 126)	Y25

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Absolute pressure (pressure series)

Selection and ordering data (continued)

Options	Order code
Add "Z" to article number, specify order code and plain text or entry from drop-down list.	
Saturation limits instead of 3.8 ... 20.5 mA, example: 3.8 ... 22.0 mA	Y30
Fault current instead of 3.6 mA [22.5 mA, 22.8 mA]	Y31
Damping in seconds instead of 2 s (0.0 ... 100.0 s)	Y32
ID number of special design	Y99

¹⁾ Explosion protection acc. to FM/CSA: suitable for installation according to NEC 500/505.

Technical specifications

SITRANS P320 / SITRANS P420 for absolute pressure (pressure series)

Input	Absolute pressure Measuring span	Max. permissible operating pressure MAWP (PS)	Maximum permissible test pressure
Measured variable Measuring span (continuously adjustable) or measuring range, max. permissible operating pressure (in accordance with Pressure Equipment Directive 2014/68/EU) and max. test pressure (pursuant to DIN 16086)	8.3 ... 250 mbar a 0.83 ... 25 kPa a 3.3 ... 100.5 inH ₂ O a 43 ... 1300 mbar a 4.3 ... 130 kPa a 17.3 ... 522 inH ₂ O a 166 ... 5 000 mbar a 16.6 ... 500 kPa a 2.41 ... 72.5 psi a 1 ... 30 bar a 0.1 ... 3 MPa a 14.5 ... 435 psi a 5.3 ... 160 bar a 0.53 ... 16 MPa a 77 ... 2321 psi a 13.3 ... 400 bar a 1.3 ... 40 MPa a 192 ... 5802 psi a 23.3 ... 700 bar a 2.3 ... 70 MPa a 337 ... 10153 psi a	4 bar a 0.4 MPa a 58 psi a 6.6 bar a 0.66 MPa a 95 psi a 20 bar a 2 MPa a 290 psi a 65 bar a 6.5 MPa a 942 psi a 240 bar 24 MPa 3481 psi 400 bar a 40 MPa a 5802 psi a 800 bar a 80 MPa a 11603 psi a	6 bar a 0.6 MPa a 87 psi a 10 bar a 1 MPa a 145 psi a 30 bar a 3 MPa a 435 psi a 100 bar a 10 MPa a 1450 psi a 380 bar a 38 MPa a 5511 psi a 600 bar a 60 MPa a 8702 psi a 800 bar a 80 MPa a 11603 psi a
Measuring limits • Lower measuring limit - Measuring cell with silicone oil filling - Measuring cell with inert oil	0 mbar a/kPa a/psi a For medium temperature -20 °C < θ ≤ +60 °C (-4 °F < θ ≤ +140 °F) For medium temperature 60 °C < θ ≤ +100 °C (max. 85 °C for measuring cell 30 bar) (140 °F < θ ≤ +212 °F (max. 185 °F for measuring cell 435 psi))		30 mbar a/3 kPa a/0.44 psi a 30 mbar a + 20 mbar a · (θ - 60 °C)/°C 3 kPa a + 2 kPa a · (θ - 60 °C)/°C 0.44 psi a + 0.29 psi a · (θ - 140 °F)/°F
• Upper measuring limit • Lower range value	100% of the max. measuring span (for oxygen measurement max. 100 bar/10 MPa/1450 psi and 60 °C (140 °F) ambient temperature/medium temperature) Between the measuring limits (continuously adjustable)		
Output	HART		
Output signal • Lower saturation limit (continuously adjustable) • Upper saturation limit (continuously adjustable) • Ripple (without HART communication)	4 ... 20 mA 3.55 mA, factory set to 3.8 mA 22.8 mA, factory-set to 20.5 mA or optionally 22.0 mA $I_{pp} \leq 0.5\%$ of max. output current		
Adjustable damping	0 ... 100 s, continuously adjustable over remote operation 0 ... 100 s, in increments of 0.1 s, adjustable over display		

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for absolute pressure (pressure series)	
• Current simulator	3.55 ... 22.8 mA
• Failure signal	3.55 ... 22.8 mA (factory set to 3.55 mA)
Load	Resistance R [Ω] $R = (U_H - 10.5 \text{ V}) / 22.8 \text{ mA}$, U _H : Auxiliary power in V
• Without HART communication	$R = 230 \dots 1100 \Omega$
• With HART communication	• Linearly increasing or linearly decreasing • Linear increase or decrease or according to the square root (only for differential pressure and flow)
Characteristic curve	
Physical bus	-
Polarity-independent	-
Measuring accuracy	
Reference conditions	• According to IEC 62828-1 • Rising characteristic curve • Lower range value 0 bar/kPa/psi • Seal diaphragm stainless steel • Measuring cell with silicone oil filling • Room temperature 25 °C (77 °F)
Conformity error at limit point setting, including hysteresis and repeatability	
Measuring span ratio r (spread, Turn-Down)	r = maximum measuring span/set measuring span or nominal measuring range
• Linear characteristic curve (all measuring cells)	
- $r \leq 10$	$\leq 0.1\%$
- $10 < r \leq 30$	$\leq 0.2\%$
Influence of ambient temperature (in % per 28 °C (50 °F))	
• 250 mbar a/25 kPa a/3.6 psi a	$\leq (0.15 \cdot r + 0.1)\%$
• 1300 mbar a/130 kPa a/18.8 psi a 5 bar a/500 kPa a/72.5 psi a 30 bar a/3000 kPa a/435 psi a 160 bar a/16 MPa a/2321 psi a 400 bar a/40 MPa a/5802 psi a 700 bar a/70 MPa a/10153 psi a	$\leq (0.08 \cdot r + 0.16)\%$
Long-term stability at $\pm 30^\circ\text{C}$ ($\pm 54^\circ\text{F}$)	In 5 years $\leq (0.25 \cdot r)\%$
Step response time T ₆₃ (without electrical damping)	Approx. 0.105 s
Effect of mounting position (in pressure per change of angle)	$\leq 0.05 \text{ mbar}/0.005 \text{ kPa}/0.000725 \text{ psi}$ per 10° incline (zero offset is possible with position error compensation)
Effect of auxiliary power (in % per voltage change)	0.005% per 1 V
Operating conditions	
Medium temperature	
• Measuring cell with silicone oil filling	-40 ... +100 °C (-40 ... +212 °F)
• Measuring cell with inert filling liquid	-20 ... +100 °C (-4 ... +212 °F)
Ambient conditions	
• Ambient temperature/enclosure	Observe the temperature class in hazardous areas.
- Measuring cell with silicone oil filling	-40 ... +85 °C (-40 ... +185 °F)
- Measuring cell with inert filling liquid	-40 ... +85 °C (-40 ... +185 °F)
- Display	-20 ... +80 °C (-4 ... +176 °F)
• Storage temperature	-50 ... +85 °C (-58 ... +185 °F) (with FDA-compliant oil: -20 ... +85 °C (-4 ... +185 °F))
• Climatic class in accordance with IEC 60721-3-4	4K4H
• Degree of protection	
- According to IEC 60529	IP66, IP68
- According to NEMA 250	Type 4X
• Electromagnetic compatibility	
- Emitted interference and interference immunity	According to IEC 61326 and NAMUR NE 21

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Absolute pressure (pressure series)

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for absolute pressure (pressure series)

Structural design	
Weight	<ul style="list-style-type: none"> • Aluminum enclosure: Approx. 1.8 kg (3.9 lbs) • Stainless steel enclosure: Approx. 3.8 kg (8.3 lbs)
Material	<ul style="list-style-type: none"> • Material of wetted parts <ul style="list-style-type: none"> - Process connection - Oval flange - Seal diaphragm • Material of non-wetted parts <ul style="list-style-type: none"> - Electronics enclosure - Mounting bracket
Process connection	<ul style="list-style-type: none"> Stainless steel, material no. 1.4404/316L or Alloy C22, material no. 2.4602 Stainless steel, mat. no. 1.4404/316L Stainless steel, material no. 1.4404/316L or Alloy C276, material no. 2.4819 • Low-copper die-cast aluminum GD-AlSi 12 or stainless steel precision casting, mat. no. 1.4409/ CF-3M • Standard: Powder coating with polyurethane Option: 2 coats: Coat 1: Epoxy-based; coat 2: Polyurethane • Stainless steel nameplate (1.4404/316L)
Electrical connection	<ul style="list-style-type: none"> Zinc-plated steel or stainless steel • Connection shank G1/2A according to EN 837-1 • Female thread 1/2-14 NPT • Oval flange (PN 160 (MWP 2320 psi g)) with fastening thread: <ul style="list-style-type: none"> - 7/16-20 UNF according to EN 61518 - M10 according to DIN 19213 • Oval flange (PN 420 (MWP 2320 psi g)) with fastening thread: <ul style="list-style-type: none"> - 7/16-20 UNF according to EN 61518 - M12 according to DIN 19213 • Male thread M20 x 1.5 and 1/2-14 NPT
Displays and controls	<ul style="list-style-type: none"> Cable entry via the following screw glands: <ul style="list-style-type: none"> • M20 x 1.5 • 1/2-14 NPT • Device plug Han 7D/Han 8D¹⁾ • Device plug M12
Buttons	4 buttons for operation directly on the device
Display	<ul style="list-style-type: none"> • With or without integrated display (optional) • Lid with inspection window (optional)
Auxiliary power U_H	
Terminal voltage on pressure transmitter	10.5 ... 45 V DC 10.5 ... 30 V DC in intrinsically safe mode
Ripple	$U_{SS} \leq 0.2 \text{ V}$ (47 ... 125 Hz)
Noise	$U_{eff} \leq 1.2 \text{ mV}$ (0.5 ... 10 kHz)
Auxiliary power	–
Separate supply voltage	–
Certificates and approvals	
Classification according to pressure equipment directive (PED 2014/68/EU)	For gases of fluid group 1 and liquids of fluid group 1; complies with requirements of article 4, paragraph 3 (sound engineering practice)
Drinking water	
• WRAS (England)	No.: 1903094 (option E83)
• ACS (France)	No.: 18 ACC LY 277 (option E85)
• NSF (USA)	No.: 20180920-MH61350 (option E84)
CRN (Canada)	No.: 0F9863.5C (option E60)
Explosion protection acc. to NEPSI (China)	No.: GYJ19.1058X (option E27)
Explosion protection acc. to INMETRO (Brazil)	No.: BRA-18-GE-0035X (option E25)
Explosion protection	
• Intrinsic safety "i"	
- Marking	II 1/2 G Ex ia(ib) IIC T4/T6 Ga/Gb

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for absolute pressure (pressure series)

- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Connection	To certified intrinsically safe circuits with peak values: $U_i = 30 \text{ V}$, $I_i = 101 \text{ mA}$, $P_i = 760 \text{ mW}$ $U_i = 29 \text{ V}$, $I_i = 110 \text{ mA}$, $P_i = 800 \text{ mW}$ $L_i = 0.24 \mu\text{H}/C_i = 3.29 \text{ nF}$
- Effective internal inductance/capacitance	
• Flameproof enclosure "d"	
- Marking	Ex II 1/2 G Ex ia/db IIC T4/T6 Ga/Gb
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Connection	To circuit with the operating values $U_n = 10.5 \dots 45 \text{ V}$, $4 \dots 20 \text{ mA}$
• Dust explosion protection for Zones 21, 22	
- Marking	Ex II 2D Ex tb IIIC T120 °C Db Ex II 3D Ex tc IIIC T120 °C Dc
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F)
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F)
- Max. surface temperature	120 °C (248 °F)
- Connection	To circuit with the operating values $U_n = 10.5 \dots 45 \text{ V}$, $4 \dots 20 \text{ mA}$
• Dust explosion protection for Zones 20, 21, 22	
- Marking	Ex II 1D Ex ia IIIC T120 °C Da Ex II 2D Ex ib IIIC T120 °C Db
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F)
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F)
- Connection	To certified intrinsically safe circuits with peak values: $U_i = 30 \text{ V}$, $I_i = 101 \text{ mA}$, $P_i = 760 \text{ mW}$ $U_i = 29 \text{ V}$, $I_i = 110 \text{ mA}$, $P_i = 800 \text{ mW}$ $L_i = 0.24 \mu\text{H}/C_i = 3.29 \text{ nF}$
- Effective internal inductance/capacitance	
• Type of protection for Zone 2	
- Marking	Ex II 3G Ex ec IIC T4/T6 Gc
- Permissible ambient temperature "ec"	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +40 °C (-40 ... +104 °F) temperature class T6
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- "ec" connection	To circuit with the operating values $U_n = 10.5 \dots 30 \text{ V}$, $4 \dots 20 \text{ mA}$
• Explosion protection acc. to FM	Available soon
- Marking (XP/DIP) or IS; NI; S	CL I, DIV 1, GP ABCD T4 ... T6; CL II, DIV 1, GP EFG; CL III; Ex ia IIC T4 ... T6: CL I, DIV 2, GP ABCD T4 ... T6; CL II, DIV 2, GP FG; CL III
• Explosion protection according to CSA	Available soon
- Marking (XP/DIP) or (IS)	CL I, DIV 1, GP ABCD T4 ... T6; CL II, DIV 1, GP EFG; CL III; Ex ia IIC T4 ... T6: CL I, DIV 2, GP ABCD T4 ... T6; CL II, DIV 2, GP FG; CL III
NAMUR recommendations	
• NE 06	Standardized Electrical Signals and Questions Relating to Engineering Technology
• NE 21	Electromagnetic Compatibility (EMC) of Industrial Process and Laboratory Control Equipment
• NE 23	Extra Low Voltage Circuits with Safe Separation
• NE 43	Standardization of the Signal Level for the Failure Information of Digital Transmitters
• NE 53	Software and Hardware of Field Devices and Signal Processing Devices with Digital Electronics
• NE 80	The Application of the Pressure Equipment Directive to Process Control Devices
• NE 105	Specifications for Integrating Fieldbus Devices in Engineering Tools for Field Devices
• NE 107	Self-Monitoring and Diagnosis of Field Devices

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Absolute pressure (pressure series)

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for absolute pressure (pressure series)

- NE 131 NAMUR Standard Device - Field Devices for Standard Applications

1) Han 8D is identical to Han 8U.

Communication	
HART	
HART	230 ... 1 100 Ω
Protocol	HART 7
Software for computer	SIMATIC PDM
PROFIBUS PA	
Simultaneous communication with master class 2 (max.)	4
The address can be set using	Configuration tool or local operation (default setting address 126)
Cyclic data usage	
• Output byte	≤ 35 (7 measured values)
• Input byte	0, 1, or 2 (register operation mode and reset function for dosing)
Internal preprocessing	
Device profile	PROFIBUS PA Profile Version 4.01 Class B. Cyclic data usage compatible with version 3.XX
Number of function blocks	7
• Analog input	
- Adaptation to user-specific process variable	Yes, linearly rising or falling characteristic curve
- Electrical damping adjustable	0 ... 100 s
- Simulation function	Output/input
- Limit monitoring	Yes, one upper and lower warning limit and one alarm limit respectively
• Register (totalizer)	Can be reset, preset, optional direction of counting, simulation function of register output
- Limit monitoring	One upper and lower warning limit and one alarm limit respectively
• Physical block	1
Transducer blocks	1
• Pressure transducer block	
- Can be calibrated by applying two pressures	Yes
- Monitoring of sensor limits	Yes
- Specification of a vessel characteristic curve with	Max. 30 nodes
- Square-rooted characteristic curve for flow measurement	Yes
- Tank characteristic curve for volume measurement	Yes
- Low flow cut-off and implementation point of square-root extraction	Parameterizable
- Simulation function for measured pressure value and sensor temperature	Constant value or by means of parameterizable ramp function
FOUNDATION Fieldbus	
Device profile	FF ITK 6
Function blocks	3 function blocks analog input, 1 function block PID
• Analog input	
- Adaptation to user-specific process variable	Yes, linearly rising or falling characteristic curve
- Electrical damping adjustable	0 ... 100 s

Technical specifications (continued)


Communication	
- Simulation function	Output/input (can be locked within the device with a bridge)
- Failure mode	Parameterizable (last good value, substitute value, incorrect value)
- Limit monitoring	Yes, one upper and lower warning limit and one alarm limit respectively
- Square-rooted characteristic curve for flow measurement	Yes
• PID	Standard FOUNDATION Fieldbus function block
• Physical block	1 resource block
Transducer blocks	1 transducer block Pressure with calibration, 1 transducer block LCD
• Pressure transducer block	
- Can be calibrated by applying two pressures	Yes
- Monitoring of sensor limits	Yes
- Simulation function: pressure measurement, sensor temperature and electronics temperature	Constant value or by means of parameterizable ramp function

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Absolute pressure (pressure series)

Dimensional drawings



SITRANS P320/P420 pressure transmitter for absolute pressure (pressure series), dimensions in mm (inch)

Selection and ordering data

	Article No.
Pressure transmitters for absolute pressure (differential pressure series)	
SITRANS P320	7MF033
SITRANS P420	7MF043
Click the article number for online configuration in the PIA Life Cycle Portal.	
Communication	
HART, 4 ... 20 mA	0
PROFIBUS PA	1
FOUNDATION Fieldbus (FF)	2
Measuring cell filling	
Silicone oil	1
Inert filling liquid	3
Maximum measuring span	
250 mbar a (100.5 inH ₂ O a)	G
1300 mbar a (522 inH ₂ O a)	L
5000 mbar a (72.5 psi a)	P
30 bar a (435 psi a)	R
160 bar (2 320 psi)	Y
Process connection	
Oval flange, fastening thread: 7/16-20 UNF (IEC 61518)	Q
Oval flange, fastening thread: M10 (DIN 19213)	R
Oval flange, fastening thread: 7/16-20 UNF (IEC 61518) with lateral ventilation	S
Oval flange, fastening thread: M10 (DIN 19213) with lateral ventilation	T
Version for diaphragm seal with fastening thread 7/16-20 UNF (IEC 61518)	V
Version for diaphragm seal with fastening thread M10 (DIN 19213)	W
Material of wetted parts: Process connection, seal diaphragm	
Stainless steel 316L/1.4404, stainless steel 316L/1.4404, process flange stainless steel 316/1.4408	0
Stainless steel 316L/1.4404, alloy C276/2.4819, process flange stainless steel 316/1.4408	1
Alloy C22/2.4602, alloy C276/2.4819, process flange stainless steel 316/1.4408	2
Tantalum/tantalum, process flange stainless steel 316/1.4408	4
Monel 400/2.4360, Monel 400/2.4360, process flange stainless steel 316/1.4408	6
Stainless steel 316L/1.4404 gold-plated, process flange stainless steel 316/1.4408	8
Material of non-wetted parts	
Die-cast aluminum	1
Stainless steel precision casting CF3M/1.4409 similar to 316L	2
Enclosure	
Dual chamber device	5
Type of protection	
Without Ex	A
Intrinsic safety	B
Flameproof enclosure	C
Flameproof enclosure, intrinsic safety	D
Dust protection by enclosure Zone 21/22 (DIP), increased safety Zone 2	L
Intrinsic safety, dust protection by enclosure Zone 20/21/22 (DIP), increased safety Zone 2	M
Combination of options B, C and L (Zone model)	S
Combination of options B, C and L (Zone model, Class Division)	T
Electrical connections/cable entries	
Thread for cable gland: Cable gland must be ordered separately as option (Axx)	
• 2 × M20 × 1.5	F
• 2 × 1/2-14 NPT	M
Local operation/display	
Without local display (lid closed)	0
With local display (lid closed)	1
With local display (lid with glass pane)	2

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Absolute pressure (differential pressure series)

Selection and ordering data (continued)

Options	Order code
Add "Z" to article no., add order code and plain text or entry from drop-down list.	
Cable glands included	
Plastic	A00
Metal	A01
Stainless steel	A02
Stainless steel 316L/1.4404	A03
CMP, for XP devices	A10
CAPRI ADE 4F, CuZn, cable inner diameter 7 ... 12 mm, cable outer diameter 10 ... 16 mm	A11
CAPRI ADE 4F, stainless steel, cable inner diameter 7 ... 12 mm, cable outer diameter 10 ... 16 mm	A12
Sealing plug included, plastic	A20
Sealing plug included, metal	A21
Sealing plug included, stainless steel	A22
Sealing plug included, stainless steel 316L/1.4404	A23
Device plug Han mounted left	
Device plug Han 7D (plastic, straight)	A30
Device plug Han 7D (plastic, angled)	A31
Device plug Han 7D (metal, straight)	A32
Device plug Han 7D (metal, angled)	A33
Device plug Han 8D (plastic, straight)	A34
Device plug Han 8D (plastic, angled)	A35
Device plug Han 8D (metal, straight)	A36
Device plug Han 8D (metal, angled)	A37
Cable socket included	
Plastic, for device plug Han 7D and Han 8D	A40
Metal, for device plug Han 7D and Han 8D	A41
Device plug M12 mounted left	
Stainless steel, without cable socket	A62
Stainless steel, with cable socket	A63
Cable entry/device plug mounting	
2x sealing plugs M20 x 1.5, IP66/68 installed on both sides	A90
2x sealing plugs ½-14 NPT, IP66/68 installed on both sides	A91
Cable gland/device plug mounted left	A97
Cable gland/device plug mounted right	A99
Nameplate labeling (standard labeling: English, unit bar)	
German (bar)	B11
French (bar)	B12
Spanish (bar)	B13
Italian (bar)	B14
Chinese (bar)	B15
Russian (bar)	B16
English (psi)	B20
English (Pa)	B30
Chinese (Pa)	B35
Certificates	
Quality inspection certificate - 5-point factory calibration (IEC 62828-2)	C11
Inspection certificate (EN 10204-3.1) - Material of pressurized and wetted parts	C12
Factory certificate - NACE (MR 0103-2012 and MR 0175-2009)	C13
Factory certificate (EN 10204-2.2) - wetted parts	C14
Inspection certificate (EN 10204-3.1) - PMI test of pressurized and wetted parts	C15

Selection and ordering data (continued)

Options	Order code
Add "Z" to article no., add order code and plain text or entry from drop-down list.	
Certificates for functional safety	
Functional Safety (IEC 61508) - SIL2/3	C20
Device options	
PDF file with device settings	D10
Double layer coating (epoxy resin and polyurethane) 120 µm of enclosure and lid	D20
FVMQ enclosure sealing	D21
IP66/IP68 degree of protection (not for device plug M12 and Han)	D30
Unlabeled TAG plate	D40
Without labeling of the measuring range on the TAG plate	D41
Stainless steel Ex plate 1.4404/316L	D42
Oversupply protection up to 6 kV (internal)	D70
Oversupply protection up to 6 kV (external)	D71
Labels on transport packaging (provided by customer)	D90
General approval without Ex approval	
Worldwide (CE, UKCA, RCM) except EAC, FM, CSA, KCC	E00
Worldwide (CE, UKCA, RCM, EAC, FM, CSA, KCC)	E01
CSA (USA and Canada)	E06
EAC	E07
FM	E08
KCC	E09
Explosion protection approvals	
ATEX (Europe)	E20
CSA (USA and Canada) ¹⁾	E21
FM (USA and Canada) ¹⁾	E22
IECEx (Worldwide)	E23
EACEx (GOST-R, -K, -B)	E24
INMETRO (Brazil)	E25
KCs (Korea)	E26
NEPSI (China)	E27
PESO (India)	E28
UKR Sepro (Ukraine)	E30
UKEX (United Kingdom)	E33
ATEX (Europe), IECEx (Worldwide) and UKEX (UK)	E47
CSA (Canada) and FM (USA) ¹⁾	E48
ATEX (Europe) and IECEx (Worldwide) + CSA (Canada) and FM (USA) ¹⁾	E49
Marine approvals	
DNV-GL (Det Norske Veritas/Germanischer Lloyd)	E50
LR (Lloyds Register)	E51
BV (Bureau Veritas)	E52
ABS (American Bureau of Shipping)	E53
RMR (Russian Maritime Register)	E55
KR (Korean Register of Shipping)	E56
RINA (Registro Italiano Navale)	E57
CCS (China Classification Society)	E58
Country-specific approvals	
CRN approval Canada (Canadian Registration Number)	E60
Special approvals	
Oxygen application (with inert liquid, max. 160 bar (2 320 psi) at 100 °C (212 °F))	E80
Dual Seal	E81

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Absolute pressure (differential pressure series)

Selection and ordering data (continued)

Options Add "Z" to article no., add order code and plain text or entry from drop-down list.	Order code
WRC/WRAS (drinking water); only with process flange O-rings made of EPDM	E83
NSF61 (drinking water)	E84
ACS (drinking water)	E85
Mounting bracket	
Steel, zinc-plated	H01
Stainless steel 1.4301/304	H02
Stainless steel 1.4404/316L	H03
Process flanges; screw plug with vent valve	
Welded in on right	J08
Welded in on left	J09
Glued in on right	J10
Glued in on left	J11
Flange connections with flange EN 1092-1	
Form B1	
• DN 25 PN 40, stainless steel 1.4571/316Ti	J70
• DN 50 PN 40, stainless steel 1.4571/316Ti	J71
• DN 80 PN 40, stainless steel 1.4571/316Ti	J72
• DN 15 PN 40, stainless steel 1.4571/316Ti	J78
Form C	
• DN 25 PN 40, stainless steel 1.4571/316Ti	J73
• DN 50 PN 40, stainless steel 1.4571/316Ti	J74
• DN 80 PN 40, stainless steel 1.4571/316Ti	J75
Flange connection options	
Flange connection and temperature extension	J76
Flange connection with epoxy resin coating	J77
Process flanges; special materials	
Reserved for 7MF7: without process flanges, without screws, without gaskets	K00
Process flange material alloy C22/2.4602	K01
Process flange material Monel 400/2.4360	K02
Process connection material PVDF, on the side 1/2-14 NPT	K05
Process flanges/process connection material PVDF, flange on the side EN 1092-1 Form B1 DN 25 PN 40, MAWP 4 bar	K06
Process flanges/process connection material PVDF, flange on the side EN 1092-1 Form B1 DN 40 PN 40, MAWP 4 bar	K07
Process flanges; process connection option	
Process flange with process connection G1½ welded on	K20
Process connection NAM (ASTAVA)	K21
Process flanges chambered with gaskets	
1 x chambered, graphite	K40
1 x chambered, PTFE (FDA-compliant), recommended for gas measurements	K41
Process flanges, gaskets (instead of standard gaskets FKM (FPM))	
O-ring, process flanges, PTFE	K50
O-ring, process flanges, FEP (with silicone core, approved for food)	K51
O-ring, process flanges, FFKM (FFPM)	K52
O-ring, process flanges, NBR	K53
O-ring, process flanges, EPDM	K54

Selection and ordering data (continued)

Options Add "Z" to article no., add order code and plain text or entry from drop-down list.	Order code
Process flange options	
Process flanges for vertical differential pressure lines (half process flange)	K81
Process flanges (+) - side front	K82
Process flange screws, process flange nuts, material Monel 400/2.4360	K83
Valve 1/4-18 NPT, material same as process flanges	K84
Valve mounted on the side, measured medium: Gas	K85
Oval flange attached, PTFE seal + fixing screws	K86
Valve manifolds	
With mounted valve manifold (3-way) 7MF9411-5BA, PTFE sealing rings, chrome-plated steel screws and pressure test certified in factory certificate (EN 10204-2.2)	U01
With mounted valve manifold (3-way) 7MF9411-5BA, PTFE sealing rings, stainless steel screws and pressure test certified in factory certificate (EN 10204-2.2)	U02
With mounted valve manifold (5-way) 7MF9411-5CA, PTFE sealing rings, chrome-plated steel screws and pressure test certified in factory certificate (EN 10204-2.2)	U03
With mounted valve manifold (5-way) 7MF9411-5CA, PTFE sealing rings, stainless steel screws and pressure test certified in factory certificate (EN 10204-2.2)	U04
Device settings	
Measuring span: Lower range value (max. 5 characters), upper range value (max. 5 characters), unit [mbar, bar, kPa, MPa, psi, ...], example: -0.5 ... 10.5 psi	Y01
TAG (on stainless steel plate and device parameters, max. 32 characters)	Y15
Measuring point description (on stainless steel plate and device parameters, max. 32 characters)	Y16
TAG short (device parameters, max. 8 characters)	Y17
Local display: [Pressure, Percent], reference [None, Absolute, Gauge], example: Pressure gauge	Y21
Local display: Scaling with standard units [m^3/s , l/s , m, inch, ...]; example 1 ... 5 m	Y22
Local display: Scaling with user-specific units (max. 12 characters), example 1 ... 5 m	Y23
Set PROFIBUS PA device address (1 ... 126)	Y25
Saturation limits instead of 3.8 ... 20.5 mA, example: 3.8 ... 22.0 mA	Y30
Fault current instead of 3.6 mA [22.5 mA, 22.8 mA]	Y31
Damping in seconds instead of 2 s (0.0 ... 100.0 s)	Y32
ID number of special design	Y99

1) Explosion protection acc. to FM/CSA: suitable for installation according to NEC 500/505.

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Absolute pressure (differential pressure series)

Technical specifications

SITRANS P320 / SITRANS P420 for absolute pressure (differential pressure series)

Input	Absolute pressure	Max. permissible operating pressure MAWP (PS)	Maximum permissible test pressure
Measured variable	Measuring span		
Measuring span (continuously adjustable) or measuring range and max. permissible operating pressure (pursuant to Pressure Equipment Directive 2014/68/EU)	8.3 ... 250 mbar a 0.83 ... 25 kPa a 3.3 ... 100.5 inH ₂ O a 43 ... 1300 mbar a 4.3 ... 130 kPa a 17.3 ... 522 inH ₂ O a 166 ... 5 000 mbar a 16.6 ... 500 kPa a 2.41 ... 72.5 psi a 1 ... 30 bar a 0.1 ... 3 MPa a 14.5 ... 435 psi a 8 ... 160 bar 0.8 ... 16 MPa 116 ... 2 320 psi	160 bar a 16 MPa a 2 320 psi a 160 bar a 16 MPa a 2 320 psi a	240 bar a 24 MPa a 3 481 psi a 240 bar a 24 MPa a 3 481 psi a
Measuring limits			
• Lower measuring limit - Measuring cell with silicone oil filling - Measuring cell with inert liquid	0 mbar a/kPa a/psi a For medium temperature -20 °C < θ ≤ +60 °C (-4 °F < θ ≤ +140 °F) For medium temperature 60 °C < θ ≤ +100 °C (max. 85 °C for measuring cell 30 bar) (140 °F < θ ≤ +212 °F (max. 185 °F for measuring cell 435 psi))	30 mbar a/3 kPa a/0.44 psi a 30 mbar a + 20 mbar a · (θ - 60 °C)/°C 3 kPa a + 2 kPa a · (θ - 60 °C)/°C 0.44 psi a + 0.29 psi a · (θ - 140 °F)/°F	
• Upper measuring limit	100% of the max. measuring span (for oxygen measurement max. 100 bar/10 MPa/1450 psi and 60 °C (140 °F) ambient temperature/medium temperature)		
• Lower range value	Between the measuring limits (continuously adjustable)		
Output	HART		
Output signal	4 ... 20 mA 3.55 mA, factory set to 3.8 mA 22.8 mA, factory-set to 20.5 mA or optionally 22.0 mA $I_{pp} \leq 0.5\%$ of max. output current		
• Lower saturation limit (continuously adjustable)	0 ... 100 s, continuously adjustable over remote operation 0 ... 100 s, in increments of 0.1 s, adjustable over display		
• Upper saturation limit (continuously adjustable)	3.55 ... 22.8 mA		
• Ripple (without HART communication)	3.55 ... 22.8 mA		
Adjustable damping	Resistance R [Ω]		
• Current simulator	R = (U _H - 10.5 V) / 22.8 mA, U _H : Auxiliary power in V		
• Failure signal	R = 230 ... 1100 Ω		
Load	• Linearly increasing or linearly decreasing • Linear increase or decrease or according to the square root (only for differential pressure and flow)		
• Without HART communication	-		
• With HART communication	-		
Characteristic curve			
Physical bus			
Polarity-independent			
Measuring accuracy			
Reference conditions	• According to IEC 62828-1 • Rising characteristic curve • Lower range value 0 bar/kPa/psi • Seal diaphragm stainless steel • Measuring cell with silicone oil filling • Room temperature 25 °C (77 °F)		
Conformity error at limit point setting, including hysteresis and repeatability			

Technical specifications (continued)**SITRANS P320 / SITRANS P420 for absolute pressure (differential pressure series)**

Measuring span ratio r (spread, Turn-Down)	r = max. measuring span/set measuring span and nominal measuring range		
• Linear characteristic curve			
- 250 mbar/25 kPa/3.63 psi	r ≤ 5:	≤ 0.075%	
	5 < r ≤ 30:	≤ (0.02 · r + 0.05)%	
- 1300 mbar a/130 kPa a/18.8 psi a 5 bar a/500 kPa a/72.5 psi a 30 bar a/3000 kPa a/435 psi a	r ≤ 5:	≤ 0.075%	
	5 < r ≤ 30:	≤ (0.005 · r + 0.05)%	
- 160 bar/16 MPa/2 320 psi	r ≤ 5:	≤ 0.075%	
	5 < r ≤ 20:	≤ (0.005 · r + 0.05)%	
Influence of ambient temperature (in % per 28 °C (50 °F))			
• 250 mbar a/25 kPa a/3.6 psi a	≤ (0.1 · r + 0.1)%		
• 1300 mbar a/130 kPa a/18.8 psi a 5 bar a/500 kPa a/72.5 psi a 30 bar a/3000 kPa a/435 psi a 160 bar a/16 MPa a/2 320 psi a	≤ (0.0025 · r + 0.125)%		
Long-term stability at ±30 °C (± 54 °F)			
• 250 mbar a/25 kPa a/3.6 psi a	In 5 years ≤ (0.2 · r)%		
• 1300 mbar a/130 kPa a/18.8 psi a 5 bar a/500 kPa a/72.5 psi a 30 bar a/3000 kPa a/435 psi a 160 bar a/16 MPa a/2 320 psi a	In 5 years ≤ (0.1 · r)% In 10 years ≤ (0.15 · r)%		
Step response time T ₆₃ (without electrical damping)			
• 250 mbar a/25 kPa a/3.6 psi a 1300 mbar a/130 kPa a/18.8 psi a 5 bar a/500 kPa a/72.5 psi a 30 bar a/3000 kPa a/435 psi a 160 bar a/16 MPa a/2 320 psi a	Every 0.135 s		
Effect of mounting position (in pressure per change of angle)	≤ 0.7 mbar/0.07 kPa/0.010 psi per 10° incline (zero offset is possible with position error compensation)		
Effect of auxiliary power (in % per voltage change)	0.005% per 1 V		
Operating conditions			
Medium temperature			
• Measuring cell with silicone oil filling	-40 ... +100 °C (-40 ... +212 °F)		
- Measuring cell 30 bar (435 psi)	-20 ... +100 °C (-4 ... +212 °F)		
- Measuring cell 160 bar (2 320 psi)	-20 ... +100 °C (-4 ... +212 °F)		
• Measuring cell with inert oil	-20 ... +100 °C (-4 ... +212 °F)		
Ambient conditions			
• Ambient temperature/enclosure	Observe the temperature class in hazardous areas.		
- Measuring cell with silicone oil filling	-40 ... +85 °C (-40 ... +185 °F)		
- Measuring cell with inert oil	-40 ... +85 °C (-40 ... +185 °F)		
- Display	-20 ... +80 °C (-4 ... +176 °F)		
• Storage temperature	-50 ... +85 °C (-58 ... +185 °F) (with FDA-compliant oil: -20 ... +85 °C (-4 ... +185 °F))		
• Climatic class in accordance with IEC 60721-3-4	4K4H		
• Degree of protection			
- According to IEC 60529	IP66, IP68		
- According to NEMA 250	Type 4X		
• Electromagnetic compatibility			
- Emitted interference and interference immunity	According to IEC 61326 and NAMUR NE 21		
Structural design			
Weight	• Aluminum enclosure: Approx. 3.9 kg (8.5 lbs) • Stainless steel enclosure: Approx. 5.9 kg (13 lbs)		
Material			

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Absolute pressure (differential pressure series)

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for absolute pressure (differential pressure series)	
• Material of wetted parts	
- Seal diaphragm	Stainless steel, mat. no. 1.4404/316L, Alloy C276, mat. no. 2.4819, Monel, mat. no. 2.4360, tantalum or gold
- Process flanges	Stainless steel, mat. no. 1.4408 to PN 160, mat. no. 1.4571/316Ti for PN 420, Alloy C22, 2.4602 or Monel, mat. no. 2.4360
- Sealing plug	1.4404 or as option alloy C22; 2.4602 or Monel mat. no. 2.4360
- O-ring	FPM (Viton) or optionally: PTFE, FEP, FEP/M and NBR
• Material of non-wetted parts	
- Electronics enclosure	<ul style="list-style-type: none"> • Low-copper die-cast aluminum GD-AISI 12 or stainless steel precision casting, mat. no. 1.4409/ CF-3M • Standard: Powder coating with polyurethane Option: 2 coats: Coat 1: Epoxy-based; coat 2: Polyurethane • Stainless steel nameplate (1.4404/316L)
- Process flange screws	Stainless steel ISO 3506-1 A4-70
- Mounting bracket	Steel, zinc-plated steel, or stainless steel
Process connection	1/4-18 NPT female thread and flange connection with 7/16-20 UNF fastening thread according to EN 61518 or M10 according to DIN 19213 (M12 for PN 420 (MWP 6092 psi))
Electrical connection	<p>Screw terminals Cable entry via the following screw glands:</p> <ul style="list-style-type: none"> • M20 × 1.5 • 1/2-14 NPT • Device plug Han 7D/Han 8D¹ • Device plug M12
Displays and controls	
Buttons	4 buttons for operation directly on the device
Display	<ul style="list-style-type: none"> • With or without integrated display (optional) • Lid with inspection window (optional)
Auxiliary power U_H	
Terminal voltage on pressure transmitter	10.5 ... 45 V DC 10.5 ... 30 V DC in intrinsically safe mode
Ripple	$U_{SS} \leq 0.2 \text{ V}$ (47 ... 125 Hz)
Noise	$U_{eff} \leq 1.2 \text{ mV}$ (0.5 ... 10 kHz)
Auxiliary power	–
Separate supply voltage	–
Certificates and approvals	
Classification according to pressure equipment directive (PED 2014/68/EU)	For gases of fluid group 1 and liquids of fluid group 1; complies with requirements of article 4, paragraph 3 (sound engineering practice)
Drinking water	
• WRAS (England)	No.: 1903094 (option E83)
• ACS (France)	No.: 18 ACC LY 277 (option E85)
• NSF (USA)	No.: 20180920-MH61350 (option E84)
CRN (Canada)	No.: OF9863.5C (option E60)
Explosion protection acc. to NEPSI (China)	No.: GYJ19.1058X (option E27)
Explosion protection acc. to INMETRO (Brazil)	No.: BRA-18-GE-0035X (option E25)
Explosion protection	
• Intrinsic safety "i"	
- Marking	II 1/2 G Ex ia(ib) IIC T4/T6 Ga/Gb
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Connection	To certified intrinsically safe circuits with peak values: $U_i = 30 \text{ V}$, $I_i = 101 \text{ mA}$, $P_i = 760 \text{ mW}$ $U_i = 29 \text{ V}$, $I_i = 110 \text{ mA}$, $P_i = 800 \text{ mW}$
- Effective internal inductance/capacitance	$L_i = 0.24 \mu\text{H}$ / $C_i = 3.29 \text{ nF}$
• Flameproof enclosure "d"	
- Marking	Ex II 1/2 G Ex ia/db IIC T4/T6 Ga/Gb

for applications with advanced requirements / SITRANS P320/420 / Absolute pressure (differential pressure series)

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for absolute pressure (differential pressure series)	
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F) temperature class T4
- Permissible medium temperature	-40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Connection	To a circuit with the operating values: $U_n = 10.5 \dots 45 V$, 4 ... 20 mA
• Dust explosion protection for zones 21, 22	
- Marking	Ex II 2D Ex tb IIIC T120 °C Db Ex II 3D Ex tc IIIC T120 °C Dc
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F)
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F)
- Max. surface temperature	120 °C (248 °F)
- Connection	To a circuit with the operating values: $U_n = 10.5 \dots 45 V$, 4 ... 20 mA
• Dust explosion protection for Zones 20, 21, 22	
- Marking	Ex II 1D Ex ia IIIC T120 °C Da Ex II 2D Ex ib IIIC T120 °C Db
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F)
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F)
- Connection	To certified intrinsically safe circuits with peak values: $U_i = 30 V$, $I_i = 101 mA$, $P_i = 760 mW$ $U_i = 29 V$, $I_i = 110 mA$, $P_i = 800 mW$ $L_i = 0.24 \mu H/C_i = 3.29 nF$
- Effective internal inductance/capacitance	
• Type of protection for Zone 2	
- Marking	Ex II 3G Ex ec IIC T4/T6 Gc
- Permissible ambient temperature "ec"	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +40 °C (-40 ... +104 °F) temperature class T6
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- "ec" connection	To a circuit with the operating values: $U_n = 10.5 \dots 30 V$, 4 ... 20 mA
• Explosion protection acc. to FM	Available soon
- Marking (XP/DIP) or IS; NI; S	CL I, DIV 1, GP ABCD T4 ... T6; CL II, DIV 1, GP EFG; CL III; Ex ia IIC T4 ... T6: CL I, DIV 2, GP ABCD T4 ... T6; CL II, DIV 2, GP FG; CL III
• Explosion protection according to CSA	Available soon
- Marking (XP/DIP) or (IS)	CL I, DIV 1, GP ABCD T4 ... T6; CL II, DIV 1, GP EFG; CL III; Ex ia IIC T4 ... T6: CL I, DIV 2, GP ABCD T4 ... T6; CL II, DIV 2, GP FG; CL III
NAMUR recommendations	
• NE 06	Standardized Electrical Signals and Questions Relating to Engineering Technology
• NE 21	Electromagnetic Compatibility (EMC) of Industrial Process and Laboratory Control Equipment
• NE 23	Extra Low Voltage Circuits with Safe Separation
• NE 43	Standardization of the Signal Level for the Failure Information of Digital Transmitters
• NE 53	Software and Hardware of Field Devices and Signal Processing Devices with Digital Electronics
• NE 80	The Application of the Pressure Equipment Directive to Process Control Devices
• NE 105	Specifications for Integrating Fieldbus Devices in Engineering Tools for Field Devices
• NE 107	Self-Monitoring and Diagnosis of Field Devices
• NE 131	NAMUR Standard Device - Field Devices for Standard Applications

¹⁾ Han 8D is identical to Han 8U.

Communication

HART	230 ... 1 100 Ω
Protocol	HART 7
Software for computer	SIMATIC PDM

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Absolute pressure (differential pressure series)


Technical specifications (continued)

Communication	
PROFIBUS PA	
Simultaneous communication with master class 2 (max.)	4
The address can be set using	Configuration tool or local operation (default setting address 126)
Cyclic data usage	≤ 35 (7 measured values)
• Output byte	
• Input byte	0, 1, or 2 (register operation mode and reset function for dosing)
Internal preprocessing	
Device profile	PROFIBUS PA Profile Version 4.01 Class B. Cyclic data usage compatible with version 3.XX
Number of function blocks	7
• Analog input	
- Adaptation to user-specific process variable	Yes, linearly rising or falling characteristic curve
- Electrical damping adjustable	0 ... 100 s
- Simulation function	Output/input
- Limit monitoring	Yes, one upper and lower warning limit and one alarm limit respectively
• Register (totalizer)	Can be reset, preset, optional direction of counting, simulation function of register output
- Limit monitoring	One upper and lower warning limit and one alarm limit respectively
• Physical block	1
Transducer blocks	1
• Pressure transducer block	
- Can be calibrated by applying two pressures	Yes
- Monitoring of sensor limits	Yes
- Specification of a vessel characteristic curve with	Max. 30 nodes
- Square-rooted characteristic curve for flow measurement	Yes
- Tank characteristic curve for volume measurement	Yes
- Low flow cut-off and implementation point of square-root extraction	Parameterizable
- Simulation function for measured pressure value and sensor temperature	Constant value or by means of parameterizable ramp function
FOUNDATION Fieldbus	
Device profile	FF ITK 6
Function blocks	3 function blocks analog input, 1 function block PID
• Analog input	
- Adaptation to user-specific process variable	Yes, linearly rising or falling characteristic curve
- Electrical damping adjustable	0 ... 100 s
- Simulation function	Output/input (can be locked within the device with a bridge)
- Failure mode	Parameterizable (last good value, substitute value, incorrect value)
- Limit monitoring	Yes, one upper and lower warning limit and one alarm limit respectively
- Square-rooted characteristic curve for flow measurement	Yes
• PID	Standard FOUNDATION Fieldbus function block
• Physical block	1 resource block

for applications with advanced requirements / SITRANS P320/420 / Absolute pressure (differential pressure series)

Technical specifications (continued)**Communication**

Transducer blocks	1 transducer block Pressure with calibration, 1 transducer block LCD
• Pressure transducer block	
- Can be calibrated by applying two pressures	Yes
- Monitoring of sensor limits	Yes
- Simulation function: pressure measurement, sensor temperature and electronics temperature	Constant value or by means of parameterizable ramp function

Dimensional drawings

SITRANS P320/P420 pressure transmitter for absolute pressure (differential pressure series), dimensions in mm (inch)

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Differential pressure and flow

Selection and ordering data

	Article No.									
Pressure transmitters for differential pressure and flow, PN 160 (MAWP 2320 psi)										
SITRANS P320	7MF034	●	-	●	●	●	●	●	●	●
SITRANS P420	7MF044	●	-	●	●	●	●	●	●	●
Click the article number for online configuration in the PIA Life Cycle Portal.										
Communication										
HART, 4 ... 20 mA	0									
PROFIBUS PA	1									
FOUNDATION Fieldbus (FF)	2									
Measuring cell filling										
Silicone oil	1									
Inert liquid	3									
Neobee oil	4									
Maximum measuring span										
20 mbar (8.037 inH ₂ O)	B									
60 mbar (24.11 inH ₂ O)	D									
250 mbar (100.5 inH ₂ O)	G									
600 mbar (241.1 inH ₂ O)	H									
1 600 mbar (643 inH ₂ O)	M									
5 000 mbar (2009 inH ₂ O)	P									
30 bar (435 psi)	R									
160 bar (2 320 psi)	Y									
Process connection										
Oval flange, fastening thread: 7/16-20 UNF (IEC 61518)	L									
Oval flange, fastening thread: M10 (PN 160) (DIN 19213)	M									
Oval flange, fastening thread: 7/16-20 UNF (IEC 61518) with lateral ventilation	N									
Oval flange, fastening thread: M10 (PN 160) (DIN 19213) with lateral ventilation	P									
Version for diaphragm seal with fastening thread 7/16-20 UNF (IEC 61518)	V									
Version for diaphragm seal with fastening thread M10 (PN 160) (DIN 19213)	W									
Version for diaphragm seal (one side mounted directly; other side with capillary line) with fastening thread 7/16-20 UNF (IEC 61518)	X									
Material of wetted parts: Process connection, seal diaphragm										
Stainless steel 316L/1.4404, stainless steel 316L/1.4404, process flange stainless steel 316/1.4408	0									
Stainless steel 316L/1.4404, alloy C276/2.4819, process flange stainless steel 316/1.4408	1									
Alloy C22/2.4602, alloy C276/2.4819, process flange stainless steel 316/1.4408	2									
Tantalum/tantalum, process flange stainless steel 316/1.4408 (not in combination with maximum measuring span 20 mbar (0.29 psi) and 60 mbar (0.87 psi))	4									
Monel 400/2.4360, Monel 400/2.4360, process flange stainless steel 316/1.4408 (not in combination with maximum measuring span 20 mbar (0.29 psi) and 60 mbar (0.87 psi))	6									
Stainless steel 316L/1.4404 gold-plated, process flange stainless steel 316/1.4408 (not in combination with maximum measuring span 20 mbar (0.29 psi) and 60 mbar (0.87 psi))	8									
Material of non-wetted parts										
Die-cast aluminum	1									
Stainless steel precision casting CF3M/1.4409 similar to 316L	2									
Enclosure										
Dual chamber device	5									
Type of protection										
Without Ex	A									
Intrinsic safety	B									
Flameproof enclosure	C									
Flameproof enclosure, intrinsic safety	D									
Dust protection by enclosure Zone 21/22 (DIP), increased safety Zone 2	L									
Intrinsic safety, dust protection by enclosure Zone 20/21/22 (DIP), increased safety Zone 2	M									
Combination of options B, C and L (Zone model)	S									
Combination of options B, C and L (Zone model, Class Division)	T									
Electrical connections/cable entries										
Thread for cable gland: Cable gland must be ordered separately as option (Axx)										
• 2 × M20 × 1.5	F									
• 2 × ½-14 NPT	M									
Local operation/display										
Without local display (lid closed)	0									
With local display (lid closed)	1									

Pressure measurement**Pressure transmitters****for applications with advanced requirements / SITRANS P320/420 / Differential pressure and flow****Selection and ordering data (continued)**

	Article No.
Pressure transmitters for differential pressure and flow, PN 160 (MAWP 2320 psi)	
SITRANS P320	7MF034
SITRANS P420	7MF044
With local display (lid with glass pane)	2
	Article No.
Pressure transmitters for differential pressure and flow, PN 420 (MAWP 6092 psi)	
SITRANS P320	7MF035
SITRANS P420	7MF045
Click the article number for online configuration in the PIA Life Cycle Portal.	
Communication	
HART, 4 ... 20 mA	0
PROFIBUS PA	1
FOUNDATION Fieldbus (FF)	2
Measuring cell filling	
Silicone oil	1
Inert liquid	3
Neobee oil	4
Maximum measuring span	
250 mbar (100.5 inH ₂ O)	G
600 mbar (241.1 inH ₂ O)	H
1600 mbar (643 inH ₂ O)	M
5000 mbar (2009 inH ₂ O)	P
30 bar (435 psi)	R
Process connection	
Oval flange, fastening thread: 7/16-20 UNF (IEC 61518)	L
Oval flange, fastening thread: M12 (PN 420) (DIN 19213)	M
Oval flange, fastening thread: 7/16-20 UNF (IEC 61518) with lateral ventilation	N
Oval flange, fastening thread: M12 (PN 420) (DIN 19213) with lateral ventilation	P
Version for diaphragm seal with fastening thread 7/16-20 UNF (IEC 61518)	V
Version for diaphragm seal with fastening thread M10 (DIN 19213)	W
Version for diaphragm seal (one side mounted directly; other side with capillary line) with fastening thread 7/16-20 UNF (IEC 61518)	X
Material of wetted parts: Process connection, seal diaphragm	
Stainless steel 316L/1.4404, stainless steel 316L/1.4404, process flange stainless steel 316/1.4408	0
Stainless steel 316L/1.4404, alloy C276/2.4819, process flange stainless steel 316/1.4408	1
Stainless steel 316L/1.4404 gold-plated, process flange stainless steel 316/1.4408	8
Material of non-wetted parts	
Die-cast aluminum	1
Stainless steel precision casting CF3M/1.4409 similar to 316L	2
Enclosure	
Dual chamber device	5
Type of protection	
Without Ex	A
Intrinsic safety	B
Flameproof enclosure	C
Flameproof enclosure, intrinsic safety	D
Dust protection by enclosure Zone 21/22 (DIP), increased safety Zone 2	L
Dust protection by enclosure Zone 20/21/22 (DIP), increased safety Zone 2	M
Combination of options B, C and L (Zone model)	S
Combination of options B, C and L (Zone model, Class Division)	T
Electrical connections/cable entries	
Thread for cable gland: Cable gland must be ordered separately as option (Axx)	
• 2 × M20 × 1.5	F
• 2 × 1/2-14 NPT	M
Local operation/display	
Without local display (lid closed)	0
With local display (lid closed)	1

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Differential pressure and flow

Selection and ordering data (continued)

	Article No.
Pressure transmitters for differential pressure and flow, PN 420 (MAWP 6092 psi)	
SITRANS P320	7MF035
SITRANS P420	7MF045
With local display (lid with glass pane)	2
Options	Order code
Add "-Z" to article no., add order code and plain text or entry from drop-down list.	
Cable glands included	
Plastic	A00
Metal	A01
Stainless steel	A02
Stainless steel 316L/1.4404	A03
CMP, for XP devices	A10
CAPRI ADE 4F, CuZn, cable inner diameter 7 ... 12 mm, cable outer diameter 10 ... 16 mm	A11
CAPRI ADE 4F, stainless steel, cable inner diameter 7 ... 12 mm, cable outer diameter 10 ... 16 mm	A12
Sealing plug included, plastic	A20
Sealing plug included, metal	A21
Sealing plug included, stainless steel	A22
Sealing plug included, stainless steel 316L/1.4404	A23
Device plug Han mounted left	
Device plug Han 7D (plastic, straight)	A30
Device plug Han 7D (plastic, angled)	A31
Device plug Han 7D (metal, straight)	A32
Device plug Han 7D (metal, angled)	A33
Device plug Han 8D (plastic, straight)	A34
Device plug Han 8D (plastic, angled)	A35
Device plug Han 8D (metal, straight)	A36
Device plug Han 8D (metal, angled)	A37
Cable socket included	
Plastic, for device plug Han 7D and Han 8D	A40
Metal, for device plug Han 7D and Han 8D	A41
Device plug M12 mounted left	
Stainless steel, without cable socket	A62
Stainless steel, with cable socket	A63
Cable entry/device plug mounting	
2 x sealing plugs M20 x 1.5, IP66/68 installed on both sides	A90
2 x sealing plugs ½-14 NPT, IP66/68 installed on both sides	A91
Cable gland/device plug mounted left	A97
Cable gland/device plug mounted right	A99
Nameplate labeling (standard labeling: English, unit bar)	
German (bar)	B11
French (bar)	B12
Spanish (bar)	B13
Italian (bar)	B14
Chinese (bar)	B15
Russian (bar)	B16
English (psi)	B20
English (Pa)	B30
Chinese (Pa)	B35

Selection and ordering data (continued)

Options Add "Z" to article no., add order code and plain text or entry from drop-down list.	Order code
Certificates	
Quality inspection certificate, 5-point factory calibration (IEC 62828-2)	C11
Inspection certificate (EN 10204-3.1) - Material of pressurized and wetted parts	C12
Factory certificate - NACE (MR 0103-2012 and MR 0175-2009)	C13
Factory certificate (EN 10204-2.2) - Wetted parts	C14
Inspection certificate (EN 10204-3.1) - PMI test of pressurized and wetted parts	C15
Certificates for functional safety	
Functional Safety (IEC 61508) - SIL2/3	C20
Device options	
PDF file with device settings	D10
Double layer coating (epoxy resin and polyurethane) 120 µm of enclosure and lid	D20
FVMQ enclosure sealing	D21
IP66/IP68 degree of protection (not for device plug M12 and Han)	D30
Unlabeled TAG plate	D40
Without labeling of the measuring range on the TAG plate	D41
Stainless steel Ex plate 1.4404/316L	D42
Increase of pressure rating from PN 420 to PN 500 (Tested according to IEC 61010. Only permissible for process media of fluid group 2 acc. to DGRL. Not suitable for use with hazardous process media.)	D50
Extension of the medium temperature to -40 °C for measuring cell filling with inert filling liquid Please note step response time T63: 5.5 s (20 and 60 mbar); 1.4 s (250 and 600 mbar); 0.3 s (1.6 and 5 bar)	D52
Overvoltage protection up to 6 kV (internal)	D70
Overvoltage protection up to 6 kV (external)	D71
Labels on transport packaging (provided by customer)	D90
General approval without Ex approval	
Worldwide (CE, UKCA, RCM) except EAC, FM, CSA, KCC	E00
Worldwide (CE, UKCA, RCM, EAC, FM, CSA, KCC)	E01
CSA (USA and Canada)	E06
EAC	E07
FM	E08
KCC	E09
Explosion protection approvals	
ATEX (Europe)	E20
CSA (USA and Canada) ¹⁾	E21
FM (USA and Canada) ¹⁾	E22
IECEx (Worldwide)	E23
EACEx (GOST-R, -K, -B)	E24
INMETRO (Brazil)	E25
KCs (Korea)	E26
NEPSI (China)	E27
PESO (India)	E28
UKR Sepro (Ukraine)	E30
UKEX (United Kingdom)	E33
ATEX (Europe), IECEx (Worldwide) and UKEX (UK)	E47
CSA (Canada) and FM (USA) ¹⁾	E48
ATEX (Europe) and IECEx (Worldwide) + CSA (Canada) and FM (USA) ¹⁾	E49

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Differential pressure and flow

Selection and ordering data (continued)

Options Add "Z" to article no., add order code and plain text or entry from drop-down list.	Order code
Marine approvals	
DNV-GL (Det Norske Veritas/Germanischer Lloyd)	E50
LR (Lloyds Register)	E51
BV (Bureau Veritas)	E52
ABS (American Bureau of Shipping)	E53
RMR (Russian Maritime Register)	E55
KR (Korean Register of Shipping)	E56
RINA (Registro Italiano Navale)	E57
CCS (China Classification Society)	E58
Country-specific approvals	
CRN approval Canada (Canadian Registration Number)	E60
Special approvals	
Oxygen application (with inert liquid, max. 160 bar (2 320 psi) at 100 °C (212 °F))	E80
Dual Seal	E81
WRC/WRAS (drinking water); only with process flange O-rings made of EPDM	E83
NSF61 (drinking water)	E84
ACS (drinking water)	E85
Mounting bracket	
Steel, zinc-plated	H01
Stainless steel 1.4301/304	H02
Stainless steel 1.4404/316L	H03
Process flanges; screw plug with vent valve	
Welded in on right	J08
Welded in on left	J09
Glued in on right	J10
Glued in on left	J11
Flange connections with flange EN 1092-1	
Form B1	
• DN 25 PN 40, stainless steel 1.4571/316Ti	J70
• DN 50 PN 40, stainless steel 1.4571/316Ti	J71
• DN 80 PN 40, stainless steel 1.4571/316Ti	J72
• DN 15 PN 40, stainless steel 1.4571/316Ti	J78
Form C	
• DN 25 PN 40, stainless steel 1.4571/316Ti	J73
• DN 50 PN 40, stainless steel 1.4571/316Ti	J74
• DN 80 PN 40, stainless steel 1.4571/316Ti	J75
Flange connection options	
Flange connection and temperature extension	J76
Flange connection with epoxy resin coating	J77
Process flanges; special materials	
Reserved for 7MF7: without process flanges, without screws, without gaskets	K00
Process flange material alloy C22/2.4602	K01
Process flange material Monel 400/2.4360	K02
Stainless steel with PVDF insert max. PN 10 (MAWP 145 psi), max. medium temperature 90 °C (194 °F)	K05
Process connection ½-14 NPT, on the side in the middle of the process flanges, no vent valves possible	
Process flanges; process connection option	
Process connection NAM (ASTAVA)	K21

Selection and ordering data (continued)

Options Add "Z" to article no., add order code and plain text or entry from drop-down list.	Order code
Process flanges chambered with gaskets	
1 x chambered, graphite	K40
1 x chambered, PTFE (FDA-compliant), recommended for gas measurements	K41
Process flanges, gaskets (instead of standard gaskets FKM (FPM))	
O-ring, process flanges, PTFE	K50
O-ring, process flanges, FEP (with silicone core, approved for food)	K51
O-ring, process flanges, FFKM (FFPM)	K52
O-ring, process flanges, NBR	K53
O-ring, process flanges, EPDM	K54
Process flange options	
Process flanges for vertical differential pressure lines (half process flange)	K81
Process flanges (+) - side front	K82
Process flange screws, process flange nuts, material Monel 400/2.4360	K83
Valve 1/4-18 NPT, material same as process flanges	K84
Valve mounted on the side, measured medium: Gas	K85
Oval flange attached, PTFE seal + fixing screws	K86
Valve manifolds	
With mounted valve manifold (3-way) 7MF9411-5BA, PTFE sealing rings, chrome-plated steel screws and pressure test certified in factory certificate (EN 10204-2.2)	U01
With mounted valve manifold (3-way) 7MF9411-5BA, PTFE sealing rings, stainless steel screws and pressure test certified in factory certificate (EN 10204-2.2)	U02
With mounted valve manifold (5-way) 7MF9411-5CA, PTFE sealing rings, chrome-plated steel screws and pressure test certified in factory certificate (EN 10204-2.2)	U03
With mounted valve manifold (5-way) 7MF9411-5CA, PTFE sealing rings, stainless steel screws and pressure test certified in factory certificate (EN 10204-2.2)	U04
Device settings	
Measuring span: Lower range value (max. 5 characters), upper range value (max. 5 characters), unit [mbar, bar, kPa, MPa, psi, ...], example: -0.5 ... 10.5 psi	Y01
Square-rooted characteristic curve [VSLN2, MSLN2]; example: VSLN2	Y02
TAG (on stainless steel plate and device parameters, max. 32 characters)	Y15
Measuring point description (on stainless steel plate and device parameters, max. 32 characters)	Y16
TAG short (device parameters, max. 8 characters)	Y17
Local display: [Pressure, Percent], reference [None, Absolute, Gauge], example: Pressure gauge	Y21
Local display: Scaling with standard units [m^3/s , l/s , m, inch, ...], example 1 ... 5 m^3/s	Y22
Local display: Scaling with user-specific units (max. 12 characters), example 1 ... 5 m	Y23
Set PROFIBUS PA device address (1 ... 126)	Y25
Saturation limits instead of 3.8 ... 20.5 mA, example: 3.8 ... 22.0 mA	Y30
Fault current instead of 3.6 mA [22.5 mA, 22.8 mA]	Y31
Damping in seconds instead of 2 s (0.0 ... 100.0 s)	Y32
ID number of special design	Y99

¹⁾ Explosion protection acc. to FM/CSA: suitable for installation according to NEC 500/505.

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Differential pressure and flow

Technical specifications

SITRANS P320 / SITRANS P420 for differential pressure and flow

Input

Measured variable

Measuring span (continuously adjustable) or measuring range and max. permissible operating pressure (pursuant to Pressure Equipment Directive 2014/68/EU)

Differential pressure and flow

Measuring span

Max. permissible operating pressure MAWP (PS)

Maximum permissible test pressure

1 ... 20 mbar	160 bar	240 bar
0.1 ... 2 kPa	16 MPa	24 MPa
0.4019 ... 8.037 inH ₂ O	2 320 psi	3 481 psi
1 ... 60 mbar	160 bar	240 bar
0.1 ... 6 kPa	16 MPa	24 MPa
0.4019 ... 24.11 inH ₂ O	2 320 psi	3 481 psi
2.5 ... 250 mbar	160 bar	240 bar
0.2 ... 25 kPa	16 MPa	24 MPa
1.005 ... 100.5 inH ₂ O	2 320 psi	3 481 psi
6 ... 600 mbar	160 bar	240 bar
0.6 ... 60 kPa	16 MPa	24 MPa
2.41 ... 241.1 inH ₂ O	2 320 psi	3 481 psi
16 ... 1600 mbar	160 bar	240 bar
1.6 ... 160 kPa	16 MPa	24 MPa
6.43 ... 643 inH ₂ O	2 320 psi	3 481 psi
50 ... 5 000 mbar	160 bar	240 bar
5 ... 500 kPa	16 MPa	24 MPa
20.09 ... 2009 inH ₂ O	2 320 psi	3 481 psi
8 ... 160 bar	160 bar	240 bar
0.8 ... 16 MPa	16 MPa	24 MPa
116 ... 2 320 psi	2 320 psi	3 481 psi
0.3 ... 30 bar	160 bar	240 bar
0.03 ... 3 MPa	16 MPa	24 MPa
4.35 ... 435 psi	2 320 psi	3 481 psi
2.5 ... 250 mbar	420 bar	630 bar
0.25 ... 25 kPa	42 MPa	63 MPa
1.005 ... 100.5 inH ₂ O	6 092 psi	9 137 psi
6 ... 600 mbar	420 bar	630 bar
0.6 ... 60 kPa	42 MPa	63 MPa
2.41 ... 241.1 inH ₂ O	6 092 psi	9 137 psi
16 ... 1600 mbar	420 bar	630 bar
1.6 ... 160 kPa	42 MPa	63 MPa
6.43 ... 643 inH ₂ O	6 092 psi	9 137 psi
50 ... 5 000 mbar	420 bar	630 bar
5 ... 500 kPa	42 MPa	63 MPa
20.09 ... 2009 inH ₂ O	6 092 psi	9 137 psi
0.3 ... 30 bar	420 bar	630 bar
0.03 ... 3 MPa	42 MPa	63 MPa
4.35 ... 435 psi	6 092 psi	9 137 psi

Measuring limits

- Lower measuring limit

- Measuring cell with silicone oil filling

All measuring cells:

- 100% of max. measuring range or 30 mbar a /3 kPa a /0.44 psi a

Measuring cell 160 bar/16 MPa/2 320 psi:

- 25% of maximum measuring range or 30 mbar a /3 kPa a /0.44 psi a

- Measuring cell with inert liquid

For medium temperature -20 °C < θ ≤ +60 °C (-4 °F < θ ≤ +140 °F)

-100% of maximum measuring range or
30 mbar a /3 kPa a /0.44 psi a

- Measuring cell with FDA-compliant oil

For medium temperature 60 °C < θ ≤ +100 °C (max. 85 °C for measuring cell 30 bar with PN 420) (140 °F < θ ≤ +212 °F (max. 185 °F for measuring cell 435 psi))

-100% of maximum measuring range or
30 mbar a /3 kPa a /0.44 psi a

- Upper measuring limit

For medium temperature -10 °C < θ ≤ +100 °C (-14 °F < θ ≤ +212 °F)

-100% of maximum measuring range or

100 mbar a /10 kPa a /14.5 psi a

100% of the max. measuring span (for oxygen measurement max. 100 bar/10 MPa/1450 psi and 60 °C (140 °F) ambient temperature/medium temperature)

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for differential pressure and flow		
• Lower range value	Between the measuring limits (continuously adjustable)	
Output	HART	
Output signal	4 ... 20 mA	
• Lower saturation limit (continuously adjustable)	3.55 mA, factory set to 3.8 mA	
• Upper saturation limit (continuously adjustable)	22.8 mA, factory-set to 20.5 mA or optionally 22.0 mA	
• Ripple (without HART communication)	$I_{pp} \leq 0.5\%$ of max. output current	
Adjustable damping	0 ... 100 s, continuously adjustable over remote operation 0 ... 100 s, in increments of 0.1 s, adjustable over local display	
• Current simulator	3.55 ... 22.8 mA	
• Failure signal	3.55 ... 22.8 mA	
Load	Resistance R [Ω] $R = (U_H - 10.5 \text{ V}) / 22.8 \text{ mA}$, U_H : Auxiliary power in V	
• Without HART communication	$R = 230 \dots 1100 \Omega$	
• With HART communication	<ul style="list-style-type: none">• Linearly increasing or linearly decreasing• Linear increase or decrease or according to the square root (only for differential pressure and flow)	
Characteristic curve		
Physical bus	-	
Polarity-independent	-	
Measuring accuracy		
Reference conditions	<ul style="list-style-type: none">• According to IEC 62828-1• Rising characteristic curve• Lower range value 0 bar/kPa/psi• Seal diaphragm stainless steel• Measuring cell with silicone oil filling• Room temperature 25 °C (77 °F)	
Characteristic curve deviation at limit point setting, including hysteresis and repeatability		
Measuring span ratio r (spread, Turn-Down)	$r = \text{maximum measuring span}/\text{set measuring span or nominal measuring range}$	
• Linear characteristic curve		
- 20 mbar/2 kPa/0.29 psi	$r \leq 5:$	$\leq 0.075\%$
	$5 < r \leq 20:$	$\leq (0.005 \cdot r + 0.05)\%$
- 60 mbar/6 kPa/0.87 psi	$r \leq 5:$	$\leq 0.075\%$
	$5 < r \leq 60:$	$\leq (0.005 \cdot r + 0.05)\%$
- 250 mbar/25 kPa/3.63 psi 600 mbar/60 kPa/8.7 psi 1600 mbar/160 kPa/23.21 psi 5 bar/500 kPa/72.5 psi 30 bar/3 MPa/435 psi	$r \leq 5:$	$\leq 0.065\%$ (SITRANS P320)
	$5 < r \leq 100:$	$\leq (0.004 \cdot r + 0.045)\%$ (SITRANS P320)
- 160 bar/16 MPa/2320 psi	$r \leq 5:$	$\leq 0.065\%$ (SITRANS P320)
	$5 < r \leq 20:$	$\leq (0.004 \cdot r + 0.045)\%$ (SITRANS P320)
- 250 mbar/25 kPa/3.63 psi (PN 160) 600 mbar/60 kPa/8.7 psi 1600 mbar/160 kPa/23.21 psi 5 bar/500 kPa/72.5 psi 30 bar/3 MPa/435 psi	$r \leq 5:$	$\leq 0.04\%$ (SITRANS P420)
	$5 < r \leq 100:$	$\leq (0.004 \cdot r + 0.045)\%$ (SITRANS P420)
- 160 bar/16 MPa/2320 psi	$r \leq 5:$	$\leq 0.04\%$ (SITRANS P420)
	$5 < r \leq 20:$	$\leq (0.004 \cdot r + 0.045)\%$ (SITRANS P420)
- 250 mbar/25 kPa/3.63 psi (PN 420)	$r \leq 5:$	$\leq 0.065\%$ (SITRANS P420)
• Square-rooted characteristic curve (flow > 50%)		
- 20 mbar/2 kPa/0.29 psi	$r \leq 5:$	$\leq 0.075\%$
	$5 < r \leq 20:$	$\leq (0.005 \cdot r + 0.05)\%$
- 60 mbar/6 kPa/0.87 psi	$r \leq 5:$	$\leq 0.075\%$
	$5 < r \leq 60:$	$\leq (0.005 \cdot r + 0.05)\%$
- 250 mbar/25 kPa/3.63 psi	$r \leq 5:$	$\leq 0.065\%$ (SITRANS P320)
		$\leq 0.04\%$ (SITRANS P420)

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Differential pressure and flow

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for differential pressure and flow		
600 mbar/60 kPa/8.7 psi 1600 mbar/160 kPa/23.21 psi 5 bar/500 kPa/72.5 psi 30 bar/3 MPa/435 psi	$5 < r \leq 100:$	$\leq (0.004 \cdot r + 0.045)\%$
- 160 bar/16 MPa/2 320 psi	$r \leq 5:$	$\leq 0.065\% \text{ (SITRANS P320)}$ $\leq 0.04\% \text{ (SITRANS P420)}$
	$5 < r \leq 20:$	$\leq (0.004 \cdot r + 0.045)\%$
• Square-rooted characteristic curve (flow 25 ... 50%)		
- 20 mbar/2 kPa/0.29 psi	$r \leq 5:$	$\leq 0.15\%$
	$5 < r \leq 20:$	$\leq (0.01 \cdot r + 0.1)\%$
- 60 mbar/6 kPa/0.87 psi	$r \leq 5:$	$\leq 0.15\%$
	$5 < r \leq 60:$	$\leq (0.01 \cdot r + 0.1)\%$
- 250 mbar/25 kPa/3.63 psi 600 mbar/60 kPa/8.7 psi 1600 mbar/160 kPa/23.21 psi 5 bar/500 kPa/72.5 psi 30 bar/3 MPa/435 psi	$r \leq 5:$	$\leq 0.13\% \text{ (SITRANS P320)}$ $\leq 0.08\% \text{ (SITRANS P420)}$
- 160 bar/16 MPa/2 320 psi	$5 < r \leq 100:$	$\leq (0.008 \cdot r + 0.09)\%$
	$r \leq 5:$	$\leq 0.13\% \text{ (SITRANS P320)}$ $\leq 0.08\% \text{ (SITRANS P420)}$
	$5 < r \leq 20:$	$\leq (0.008 \cdot r + 0.09)\%$
Influence of ambient temperature (in % per 28 °C (50 °F))		
- 20 mbar/2 kPa/0.29 psi		$\leq (0.15 \cdot r + 0.1)\%$
- 60 mbar/6 kPa/0.87 psi		$\leq (0.075 \cdot r + 0.1)\%$
- 250 mbar/25 kPa/3.63 psi 600 mbar/60 kPa/8.7 psi 1600 mbar/160 kPa/23.21 psi 5 bar/500 kPa/72.5 psi 30 bar/3 MPa/435 psi 160 bar/16 MPa/2 320 psi		$\leq (0.025 \cdot r + 0.125)\% \text{ (SITRANS P320)}$
- 250 mbar/25 kPa/3.63 psi 5 bar/500 kPa/72.5 psi		$\leq (0.025 \cdot r + 0.0625)\% \text{ (SITRANS P420)}$
- 600 mbar/60 kPa/8.7 psi 1600 mbar/160 kPa/23.21 psi 30 bar/3 MPa/435 psi 160 bar/16 MPa/2 320 psi		$\leq (0.0125 \cdot r + 0.0625)\% \text{ (SITRANS P420)}$
Effect of static pressure		
• At the lower range value		Zero offset is possible with position error compensation
- 20 mbar/2 kPa/0.29 psi		$\leq (0.3 \cdot r)\% \text{ per 70 bar (SITRANS P320)}$ $\leq (0.2 \cdot r)\% \text{ per 70 bar (SITRANS P420)}$
- 60 mbar/6 kPa/0.87 psi 250 mbar/25 kPa/3.63 psi 600 mbar/60 kPa/8.7 psi 1600 mbar/160 kPa/23.21 psi 30 bar/3 MPa/435 psi 160 bar/16 MPa/2 320 psi		$\leq (0.1 \cdot r)\% \text{ per 70 bar}$
- 5 bar/500 kPa/72.5 psi		$\leq (0.15 \cdot r)\% \text{ per 70 bar}$
• On the measuring span		
- 20 mbar/2 kPa/0.29 psi		$\leq 0.2\% \text{ per 70 bar}$
- 60 mbar/6 kPa/0.87 psi 250 mbar/25 kPa/3.63 psi 600 mbar/60 kPa/8.7 psi 1600 mbar/160 kPa/23.21 psi 5 bar/500 kPa/72.5 psi 30 bar/3 MPa/435 psi 160 bar/16 MPa/2 320 psi		$\leq 0.1\% \text{ per 70 bar}$
Long-term stability at $\pm 30^\circ\text{C}$ ($\pm 54^\circ\text{F}$)		Static pressure max. 70 bar/7 MPa/1015 psi

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for differential pressure and flow	
• 20 mbar/2 kPa/0.29 psi	$\leq (0.2 \cdot r)\%$ per year
• 60 mbar/6 kPa/0.87 psi	In 5 years $\leq (0.25 \cdot r)\%$
• 250 mbar/25 kPa/3.63 psi 600 mbar/60 kPa/8.7 psi 1600 mbar/160 kPa/23.21 psi 5 bar/500 kPa/72.5 psi 160 bar/16 MPa/2 320 psi	In 5 years $\leq (0.125 \cdot r)\%$ In 10 years $\leq (0.15 \cdot r)\%$
• 30 bar/3 MPa/435 psi	In 5 years $\leq (0.25 \cdot r)\%$ In 10 years $\leq (0.35 \cdot r)\%$
Step response time T_{63} (without electrical damping for pressure rating PN 160)	
• 20 mbar/2 kPa/0.29 psi	Approx. 0.160 s
• 60 mbar/6 kPa/0.87 psi	Approx. 0.150 s
• 250 mbar/25 kPa/3.63 psi 600 mbar/60 kPa/8.7 psi 1600 mbar/160 kPa/23.21 psi 5 bar/500 kPa/72.5 psi 30 bar/3 MPa/435 psi 160 bar/16 MPa/2 320 psi	Approx. 0.135 s
Effect of mounting position (in pressure per change of angle)	$\leq 0.7 \text{ mbar}/0.07 \text{ kPa}/0.028 \text{ inH}_2\text{O}$ per 10° incline (zero offset is possible with position error compensation)
Effect of auxiliary power (in % per voltage change)	0.005% per 1 V
Operating conditions	
Medium temperature	
• Measuring cell with silicone oil filling	-40 ... +100 °C (-40 ... +212 °F)
- Measuring cell 30 bar (435 psi)	-20 ... +100 °C (-4 ... +212 °F)
- Measuring cell 160 bar (2 320 psi)	-20 ... +100 °C (-4 ... +212 °F)
• Measuring cell with inert oil	-20 ... +100 °C (-4 ... +212 °F)
• Measuring cell with FDA-compliant oil	-10 ... +100 °C (14 ... +212 °F)
Ambient conditions	
• Ambient temperature/enclosure	Observe the temperature class in hazardous areas.
- Measuring cell with silicone oil filling	-40 ... +85 °C (-40 ... +185 °F)
- Measuring cell with inert oil	-40 ... +85 °C (-40 ... +185 °F)
- Measuring cell with FDA-compliant oil	-10 ... +85 °C (14 ... +185 °F)
- Local display	-20 ... +80 °C (-4 ... +176 °F)
• Storage temperature	-50 ... +85 °C (-58 ... +185 °F) (with FDA-compliant oil: -20 ... +85 °C (-4 ... +185 °F))
• Climatic class in accordance with IEC 60721-3-4	4K4H
• Degree of protection	
- According to IEC 60529	IP66, IP68
- According to NEMA 250	Type 4X
• Electromagnetic compatibility	
- Emitted interference and interference immunity	According to IEC 61326 and NAMUR NE 21
Structural design	
Weight	<ul style="list-style-type: none"> Aluminum enclosure: Approx. 3.9 kg (8.5 lbs) Stainless steel enclosure: Approx. 5.9 kg (13 lbs)
Material	
• Material of wetted parts	
- Seal diaphragm	Stainless steel, mat. no. 1.4404/316L, Alloy C276, mat. no. 2.4819, Monel, mat. no. 2.4360, tantalum or gold
- Process flanges	Stainless steel, mat. no. 1.4408 to PN 160, mat. no. 1.4571/316Ti for PN 420, Alloy C22, 2.4602 or Monel, mat. no. 2.4360
- Sealing plug	1.4404 or as option alloy C22; 2.4602 or Monel mat. no. 2.4360
- O-ring	FPM (Viton) or optionally: PTFE, FEP, FEPM and NBR
• Material of non-wetted parts	

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Differential pressure and flow

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for differential pressure and flow

- Electronics enclosure	<ul style="list-style-type: none"> Low-copper die-cast aluminum GD-AlSi 12 or stainless steel precision casting, mat. no. 1.4409/ CF-3M Standard: Powder coating with polyurethane Option: 2 coats: Coat 1: Epoxy-based; coat 2: Polyurethane Stainless steel nameplate (1.4404/316L)
- Process flange screws	Stainless steel ISO 3506-1 A4-70
- Mounting bracket	Steel, zinc-plated steel, or stainless steel
Process connection	1/4-18 NPT internal thread and flange connection with 7/16-20 UNF fastening thread according to EN 61518 or M10 according to DIN 19213 (M12 for PN 420 (MWP 6 092 psi))
Electrical connection	<p>Screw terminals Cable entry via the following screw glands:</p> <ul style="list-style-type: none"> M20 × 1.5 1/2-14 NPT Device plug Han 7D/Han 8D¹⁾ Device plug M12
Displays and controls	
Buttons	4 buttons for operation directly on the device
Local display	<ul style="list-style-type: none"> With or without integrated local display (optional) Lid with inspection window (optional)
Auxiliary power U_H	
Terminal voltage on pressure transmitter	10.5 ... 45 V DC 10.5 ... 30 V DC in intrinsically safe mode
Ripple	U _{SS} ≤ 0.2 V (47 ... 125 Hz)
Noise	U _{eff} ≤ 1.2 mV (0.5 ... 10 kHz)
Auxiliary power	–
Separate supply voltage	–
Certificates and approvals	
Classification according to pressure equipment directive (PED 2014/68/EU)	For gases of fluid group 1 and liquids of fluid group 1; complies with requirements of article 4, paragraph 3 (sound engineering practice) For flow only For gases of fluid group 1 and liquids of fluid group 1; fulfills the basic safety requirements as per article 3, paragraph 1 (appendix 1); classified as category III, module H conformity evaluation by TÜV Nord
Drinking water	No.: 1903094 (option E83)
• WRAS (England)	No.: 18 ACC LY 277 (option E85)
• ACS (France)	No.: 20180920-MH61350 (option E84)
• NSF (USA)	No.: 0F9863.5C (option E60)
CRN (Canada)	No.: GYJ19.1058X (option E27)
Explosion protection acc. to NEPSI (China)	No.: BRA-18-GE-0035X (option E25)
Explosion protection acc. to INMETRO (Brazil)	
Explosion protection	
• Intrinsic safety "i"	II 1/2 G Ex ia/b IIC T4/T6 Ga/Gb
- Marking	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Permissible ambient temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Permissible medium temperature	To certified intrinsically safe circuits with peak values: U _i = 30 V, I _i = 101 mA, P _i = 760 mW U _i = 29 V, I _i = 110 mA, P _i = 800 mW
- Connection	L _i = 0.24 µH/C _i = 3.29 nF
- Effective internal inductance/capacitance	Ex II 1/2 G Ex ia/db IIC T4/T6 Ga/Gb
• Flameproof enclosure "d"	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Marking	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Permissible ambient temperature	To a circuit with the operating values: U _n = 10.5 ... 45 V, 4 ... 20 mA
- Permissible medium temperature	
- Connection	

Technical specifications (continued)**SITRANS P320 / SITRANS P420 for differential pressure and flow**

• Dust explosion protection for Zones 21, 22	
- Marking	Ex II 2D Ex tb IIIC T120 °C Db Ex II 3D Ex tc IIIC T120 °C Dc
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F)
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F)
- Max. surface temperature	120 °C (248 °F)
- Connection	To a circuit with the operating values: $U_n = 10.5 \dots 45 V$, $4 \dots 20 mA$
• Dust explosion protection for Zones 20, 21, 22	
- Marking	Ex II 1D Ex ia IIIC T120 °C Da Ex II 2D Ex ib IIIC T120 °C Db
- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F)
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F)
- Connection	To certified intrinsically safe circuits with peak values: $U_i = 30 V$, $I_i = 101 mA$, $P_i = 760 mW$ $U_i = 29 V$, $I_i = 110 mA$, $P_i = 800 mW$ $L_i = 0.24 \mu H/C_i = 3.29 nF$
• Type of protection for Zone 2	
- Marking	Ex II 3G Ex ec IIC T4/T6 Gc
- Permissible ambient temperature "ec"	-40 ... +80 °C (-40 ... +176 °F) temperature class T4 -40 ... +40 °C (-40 ... +104 °F) temperature class T6
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4 -40 ... +70 °C (-40 ... +158 °F) temperature class T6
- "ec" connection	To a circuit with the operating values: $U_n = 10.5 \dots 30 V$, $4 \dots 20 mA$
• Explosion protection acc. to FM	Available soon
- Marking (XP/DIP) or IS; NI; S	CL I, DIV 1, GP ABCD T4 ... T6; CL II, DIV 1, GP EFG; CL III; Ex ia IIC T4 ... T6: CL I, DIV 2, GP ABCD T4 ... T6; CL II, DIV 2, GP FG; CL III
• Explosion protection according to CSA	Available soon
- Marking (XP/DIP) or (IS)	CL I, DIV 1, GP ABCD T4 ... T6; CL II, DIV 1, GP EFG; CL III; Ex ia IIC T4 ... T6: CL I, DIV 2, GP ABCD T4 ... T6; CL II, DIV 2, GP FG; CL III
NAMUR recommendations	
• NE 06	Standardized Electrical Signals and Questions Relating to Engineering Technology
• NE 21	Electromagnetic Compatibility (EMC) of Industrial Process and Laboratory Control Equipment
• NE 23	Extra Low Voltage Circuits with Safe Separation
• NE 43	Standardization of the signal level for the failure information of digital transmitters with analog output signal
• NE 53	Software and Hardware of Field Devices and Signal Processing Devices with Digital Electronics
• NE 80	The Application of the Pressure Equipment Directive to Process Control Devices
• NE 105	Specifications for Integrating Fieldbus Devices in Engineering Tools for Field Devices
• NE 107	Self-Monitoring and Diagnosis of Field Devices
• NE 131	NAMUR Standard Device - Field Devices for Standard Applications

Communication

HART	
HART	230 ... 1 100 Ω
Protocol	HART 7
Software for computer	SIMATIC PDM
PROFIBUS PA	
Simultaneous communication with master class 2 (max.)	4
The address can be set using	Configuration tool or local operation (default setting address 126)
Cyclic data usage	≤ 35 (7 measured values)
• Output byte	0, 1, or 2 (register operation mode and reset function for dosing)
• Input byte	

Pressure measurement


Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Differential pressure and flow

Technical specifications (continued)

Communication	
Internal preprocessing	
Device profile	PROFIBUS PA Profile Version 4.01 Class B. Cyclic data usage compatible with version 3.XX
Number of function blocks	7
• Analog input	
- Adaptation to user-specific process variable	Yes, linearly rising or falling characteristic curve
- Electrical damping adjustable	0 ... 100 s
- Simulation function	Output/input
- Limit monitoring	Yes, one upper and lower warning limit and one alarm limit respectively
• Register (totalizer)	Can be reset, preset, optional direction of counting, simulation function of register output
- Limit monitoring	One upper and lower warning limit and one alarm limit respectively
• Physical block	1
Transducer blocks	1
• Pressure transducer block	
- Can be calibrated by applying two pressures	Yes
- Monitoring of sensor limits	Yes
- Specification of a vessel characteristic curve with	Max. 30 nodes
- Square-rooted characteristic curve for flow measurement	Yes
- Tank characteristic curve for volume measurement	Yes
- Low flow cut-off and implementation point of square-root extraction	Parameterizable
- Simulation function for measured pressure value and sensor temperature	Constant value or by means of parameterizable ramp function
FOUNDATION Fieldbus	
Device profile	FF ITK 6
Function blocks	3 function blocks analog input, 1 function block PID
• Analog input	
- Adaptation to user-specific process variable	Yes, linearly rising or falling characteristic curve
- Electrical damping adjustable	0 ... 100 s
- Simulation function	Output/input (can be locked within the device with a bridge)
- Failure mode	Parameterizable (last good value, substitute value, incorrect value)
- Limit monitoring	Yes, one upper and lower warning limit and one alarm limit respectively
- Square-rooted characteristic curve for flow measurement	Yes
• PID	Standard FOUNDATION Fieldbus function block
• Physical block	1 resource block
Transducer blocks	1 transducer block Pressure with calibration, 1 transducer block LCD
• Pressure transducer block	
- Can be calibrated by applying two pressures	Yes
- Monitoring of sensor limits	Yes
- Simulation function: pressure measurement, sensor temperature and electronics temperature	Constant value or by means of parameterizable ramp function

Dimensional drawings




SITRANS P320/P420 pressure transmitter for differential pressure and flow, dimensions in mm (inch)

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Differential pressure and flow

Dimensional drawings (continued)



SITRANS P320/P420 pressure transmitter for differential pressure and flow with process covers for vertical differential pressure lines (option "K81"), dimensions in mm (inch)

Selection and ordering data

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Level

Selection and ordering data (continued)

Options Add "Z" to article number, specify order code and plain text or entry from drop-down list.	Order code
Stainless steel	A02
Stainless steel 316L/1.4404	A03
CMP, for XP devices	A10
CAPRI ADE 4F, CuZn, cable inner diameter 7 ... 12 mm, cable outer diameter 10 ... 16 mm	A11
CAPRI ADE 4F, stainless steel, cable inner diameter 7 ... 12 mm, cable outer diameter 10 ... 16 mm	A12
Sealing plug included, plastic	A20
Sealing plug included, metal	A21
Sealing plug included, stainless steel	A22
Sealing plug included, stainless steel 316L/1.4404	A23
Device plug Han mounted left	
Device plug Han 7D (plastic, straight)	A30
Device plug Han 7D (plastic, angled)	A31
Device plug Han 7D (metal, straight)	A32
Device plug Han 7D (metal, angled)	A33
Device plug Han 8D (plastic, straight)	A34
Device plug Han 8D (plastic, angled)	A35
Device plug Han 8D (metal, straight)	A36
Device plug Han 8D (metal, angled)	A37
Cable socket included	
Plastic, for device plug Han 7D and Han 8D	A40
Metal, for device plug Han 7D and Han 8D	A41
Device plug M12 mounted left	
Stainless steel, without cable socket	A62
Stainless steel, with cable socket	A63
Cable entry/device plug mounting	
2x sealing plugs M20 x 1.5, IP66/68 installed on both sides	A90
2x sealing plugs ½-14 NPT, IP66/68 installed on both sides	A91
Cable gland/device plug mounted left	A97
Cable gland/device plug mounted right	A99
Nameplate labeling (standard labeling: English, unit bar)	
German (bar)	B11
French (bar)	B12
Spanish (bar)	B13
Italian (bar)	B14
Chinese (bar)	B15
Russian (bar)	B16
English (psi)	B20
English (Pa)	B30
Chinese (Pa)	B35
Certificates	
Quality inspection certificate, 5-point factory calibration (IEC 62828-2)	C11
Inspection certificate (EN 10204-3.1) - Material of pressur- ized and wetted parts	C12
Factory certificate - NACE (MR 0103-2012 and MR 0175-2009)	C13
Factory certificate (EN 10204-2.2) - Wetted parts	C14
Inspection certificate (EN 10204-3.1) - PMI test of pressur- ized and wetted parts	C15
Certificates for functional safety	
Functional Safety (IEC 61508) - SIL2/3	C20

Selection and ordering data (continued)

Options Add "Z" to article number, specify order code and plain text or entry from drop-down list.	Order code
Device options	
PDF file with device settings	D10
Double layer coating (epoxy resin and polyurethane) 120 µm of enclosure and lid	D20
FVMQ enclosure sealing	D21
IP66/IP68 degree of protection (not for device plug M12 and Han)	D30
Unlabeled TAG plate	D40
Without labeling of the measuring range on the TAG plate	D41
Stainless steel Ex plate 1.4404/316L	D42
Oversupply protection up to 6 kV (internal)	D70
Oversupply protection up to 6 kV (external)	D71
Labels on transport packaging (provided by customer)	D90
General approval without Ex approval	
Worldwide (CE, UKCA, RCM) except EAC, FM, CSA, KCC	E00
Worldwide (CE, UKCA, RCM, EAC, FM, CSA, KCC)	E01
CSA (USA and Canada)	E06
EAC	E07
FM	E08
KCC	E09
Explosion protection approvals	
ATEX (Europe)	E20
CSA (USA and Canada) ¹⁾	E21
FM (USA and Canada) ¹⁾	E22
IECEx (Worldwide)	E23
EACEx (GOST-R, -K, -B)	E24
INMETRO (Brazil)	E25
KCs (Korea)	E26
NEPSI (China)	E27
PESO (India)	E28
UKR Sepro (Ukraine)	E30
UKEX (United Kingdom)	E33
ATEX (Europe), IECEx (Worldwide) and UKEX (UK)	E47
CSA (Canada) and FM (USA) ¹⁾	E48
ATEX (Europe) and IECEx (Worldwide) + CSA (Canada) and FM (USA) ¹⁾	E49
Marine approvals	
DNV-GL (Det Norske Veritas/Germanischer Lloyd)	E50
LR (Lloyds Register)	E51
BV (Bureau Veritas)	E52
ABS (American Bureau of Shipping)	E53
RMR (Russian Maritime Register)	E55
KR (Korean Register of Shipping)	E56
RINA (Registro Italiano Navale)	E57
CCS (China Classification Society)	E58
Country-specific approvals	
CRN approval Canada (Canadian Registration Number)	E60
Special approvals	
Oxygen application (with inert liquid, max. 160 bar (2 320 psi) at 100 °C (212 °F))	E80
Dual Seal	E81

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Level

Selection and ordering data (continued)

Options	Order code
Add "Z" to article number, specify order code and plain text or entry from drop-down list.	
WRC/WRAS (drinking water); only with process flange O-rings made of EPDM	E83
NSF61 (drinking water)	E84
ACS (drinking water)	E85
Process flanges	
Gasket process flange 1 x chambered, graphite	K40
Gasket process flange, 1 x chambered, PTFE	K41
Vent valve in the material of the process flange	K84
Device settings	
Measuring span: Lower range value (max. 5 characters), upper range value (max. 5 characters), unit [mbar, bar, kPa, MPa, psi, ...], example: -0.5 ... 10.5 psi	Y01
TAG (on stainless steel plate and device parameters, max. 32 characters)	Y15
Measuring point description (on stainless steel plate and device parameters, max. 32 characters)	Y16
TAG short (device parameters, max. 8 characters)	Y17
Local display: [Pressure, Percent], reference [None, Absolute, Gauge], example: Pressure gauge	Y21
Local display: Scaling with standard units [m^3/s , l/s, m, inch, ...]; example 1 ... 5 m	Y22
Local display: Scaling with user-specific units (max. 12 characters), example 1 ... 5 m	Y23
Set PROFIBUS PA device address (1 ... 126)	Y25
Saturation limits instead of 3.8 ... 20.5 mA, example: 3.8 ... 22.0 mA	Y30
Fault current instead of 3.6 mA [22.5 mA, 22.8 mA]	Y31
Damping in seconds instead of 2 s (0.0 ... 100.0 s)	Y32
ID number of special design	Y99

¹⁾ Explosion protection acc. to FM/CSA: suitable for installation according to NEC 500/505.

Diaphragm seal In flange design, directly installed on a pressure transmitter for level SITRANS P320/P420 7MF03../7MF04.. to be ordered separately, scope of delivery: 1 unit	Article No. 7MF0814-	Order code ● ● ● 0 3 - 0 ● ● ● ● ● ●
Click the article number for online configuration in the PIA Life Cycle Portal.		
Standard of process connection EN 1092-1		
Nominal diameter	Nominal pressure	
DN 25	PN 10/16/25/40 PN 63/100 PN 160 PN 250	0 B D 0 B F 0 B G 0 B H
DN 40	PN 10/16/25/40 PN 63/100 PN 160	0 D D 0 D F 0 D G
DN 50	PN 10/16/25/40 PN 63/100 PN 160	0 E D 0 E E 0 E F
DN 80	PN 10/16/25/40 PN 100	0 G D 0 G F
DN 100	PN 10/16 PN 25/40	0 H B 0 H D
DN 125	PN 16 PN 40	0 J B 0 J D
Process connection standard ASME B16.5		
Nominal diameter	Nominal pressure	
1 inch	Class 150	1 K L

Selection and ordering data (continued)

		Article No.	Order code
		7MF0814-	
Diaphragm seal In flange design, directly installed on a pressure transmitter for level SITRANS P320/P420 7MF03../7MF04.. to be ordered separately, scope of delivery: 1 unit		• • • 0 3 - 0 • • •	• • •
	Class 300	1 K M	
	Class 600	1 K N	
	Class 1500	1 K P	
1½ inches	Class 150	1 L A	
	Class 300	1 L B	
	Class 400/600	1 L D	
	Class 900/1500	1 L F	
2 inches	Class 150	1 M A	
	Class 300	1 M B	
	Class 400/600	1 M D	
	Class 900/1500	1 M F	
3 inches	Class 150	1 P A	
	Class 300	1 P B	
	Class 600	1 P D	
	Class 1500	1 P F	
4 inches	Class 150	1 Q A	
	Class 300	1 Q B	
	Class 400	1 Q D	
	Class 1500	1 Q F	
5 inches	Class 150	1 R A	
	Class 300	1 R B	
	Class 400	1 R C	
Process connection standard J.I.S.			
Nominal diameter		Nominal pressure	
DN 50	10K	2 E S	
	20k	2 E T	
	40K	2 E U	
DN 80	10K	2 G S	
	20k	2 G T	
	40K	2 G U	
DN 100	10K	2 H S	
	20k	2 H T	
	40K	2 H U	
Other version, add order code and plain text		9 Z A	H 1 Y
Filling liquid			
Silicone oil M50			B
High-temperature oil			C
Silicone oil M5			A
Food oil (FDA-listed)			E
Neobee M20 (FDA-listed)			R
Halocarbon oil			D
Other version, add order code and plain text			Z
Material of wetted parts			
Stainless steel 316L			A
• Without coating			
• With PFA coating			D
• With PTFE coating			E O
• With ECTFE coating			F
Monel 400, 2.4360			G
Hastelloy C276, 2.4819			J
Tantalum			K
Titanium, 3.7035			L O
Nickel 201			M O
Diaphragm Duplex, 1.4462			Q

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Level

Selection and ordering data (continued)

	Article No.	Order code
	7MF0814-	
Diaphragm seal In flange design, directly installed on a pressure transmitter for level SITRANS P320/P420 7MF03../7MF04.. to be ordered separately, scope of delivery: 1 unit	• • • 0 3 - 0 • • •	• • •
Diaphragm and flange Duplex, 1.4462	R	
Stainless steel 316L, gold-plated	S 0	
Hastelloy C4, 2.4610	U 0	
Hastelloy C22, 2.4602	V 0	
Other version, add order code and plain text	Z	Q 1 Y
Tube length		
None		0
50 mm (2 inches)		1
100 mm (4 inches)		2
150 mm (6 inches)		3
200 mm (8 inches)		4
250 mm (10 inches)		5
Other version, add order code and plain text	Z 8	R 1 Y
Customer-specific tube length		
• Wetted parts: Stainless steel without coating		
Range	Standard length	
20 ... 50 mm (0.79 ... 1.97 inches)	50 mm (1.97 inches)	A 1
51 ... 100 mm (2.01 ... 3.94 inches)	100 mm (3.94 inches)	A 2
101 ... 150 mm (3.98 ... 5.91 inches)	150 mm (5.91 inches)	A 3
151 ... 200 mm (5.94 ... 7.87 inches)	200 mm (7.87 inches)	A 4
201 ... 250 mm (7.91 ... 9.84 inches)	250 mm (9.84 inches)	A 5
• Wetted parts: Stainless steel with ECTFE coating		
Range	Standard length	
20 ... 50 mm (0.79 ... 1.97 inches)	50 mm (1.97 inches)	F 1
51 ... 100 mm (2.01 ... 3.94 inches)	100 mm (3.94 inches)	F 2
101 ... 150 mm (3.98 ... 5.91 inches)	150 mm (5.91 inches)	F 3
151 ... 200 mm (5.94 ... 7.87 inches)	200 mm (7.87 inches)	F 4
201 ... 250 mm (7.91 ... 9.84 inches)	250 mm (9.84 inches)	F 5
• Wetted parts: Stainless steel with PFA coating		
Range	Standard length	
20 ... 50 mm (0.79 ... 1.97 inches)	50 mm (1.97 inches)	D 1
51 ... 100 mm (2.01 ... 3.94 inches)	100 mm (3.94 inches)	D 2
101 ... 150 mm (3.98 ... 5.91 inches)	150 mm (5.91 inches)	D 3
151 ... 200 mm (5.94 ... 7.87 inches)	200 mm (7.87 inches)	D 4
201 ... 250 mm (7.91 ... 9.84 inches)	250 mm (9.84 inches)	D 5
• Wetted parts: Monel 400		
Range	Standard length	
20 ... 50 mm (0.79 ... 1.97 inches)	50 mm (1.97 inches)	G 1
51 ... 100 mm (2.01 ... 3.94 inches)	100 mm (3.94 inches)	G 2
101 ... 150 mm (3.98 ... 5.91 inches)	150 mm (5.91 inches)	G 3
151 ... 200 mm (5.94 ... 7.87 inches)	200 mm (7.87 inches)	G 4
• Wetted parts: Hastelloy C276		
Range	Standard length	
20 ... 50 mm (0.79 ... 1.97 inches)	50 mm (1.97 inches)	J 1
51 ... 100 mm (2.01 ... 3.94 inches)	100 mm (3.94 inches)	J 2
101 ... 150 mm (3.98 ... 5.91 inches)	150 mm (5.91 inches)	J 3
151 ... 200 mm (5.94 ... 7.87 inches)	200 mm (7.87 inches)	J 4
• Wetted parts: Tantalum		
Range	Standard length	
20 ... 50 mm (0.79 ... 1.97 inches)	50 mm (1.97 inches)	K 1
51 ... 100 mm (2.01 ... 3.94 inches)	100 mm (3.94 inches)	K 2
101 ... 150 mm (3.98 ... 5.91 inches)	150 mm (5.91 inches)	K 3
151 ... 200 mm (5.94 ... 7.87 inches)	200 mm (7.87 inches)	K 4

Selection and ordering data (continued)

Options Add "Z" to article number, specify order code and plain text or entry from drop-down list.	Order code
Factory certificates	
Quality inspection certificate (5-point characteristic curve test) according to IEC 62828-2	C11
Inspection certificate according to EN 10204-3.1 for main body and diaphragm	C12
Manufacturer code according to NACE (MR 0103-2012 and MR 0175-2009) (only in combination with wetted parts made of stainless steel 316 L and Hastelloy)	C13
Inspection certificate according to EN 10204-3.1, PMI test of pressure containing and wetted parts	C15
Test report on the FDA listing of the oil according to EN 10204-2.2	C17
Factory certificate functional safety (SIL2/3), suitability of devices for use according to IEC 61508 and IEC 61511 (contains SIL Declaration of Conformity)	C20
Accessories	
Epoxy resin coating Color: Transparent Scope: Front and rear of the remote seal, connecting pipe, process connection of the transmitter. Maximum medium temperature with epoxy resin coating: 140 °C	D15
Remote seal nameplate Attached, made of stainless steel, contains Article No. and order number of the remote seal	D42
Volume deflagration flame arrester (VDEF) for differential pressure transmitter	D62
Negative pressure service	
Negative pressure service for differential pressure transmitters	D83
Extended negative pressure service for differential pressure transmitters	D88
Approvals and certificates	
Country-specific approval CRN approval Canada (Canadian Registration Number)	E60
Note: If the order code E60 is selected, the option E60 must also be selected for the transmitter!	
Oil-free and grease-free cleaned version for oxygen application including EN 10204-2.2 certificates (only with filling liquid halocarbon oil and at max. temperature 60 °C and max. pressure 50 bar)	E80
Oil-free and grease-free cleaned version not for oxygen application, including EN 10204-2.2 certificates	E87
Sealing surface	
Sealing surface smooth, form B2/EN1092-1 or RFSF/ANSI 16.5 (only for wetted parts made of stainless steel 316L)	M50
Sealing surface groove according to EN 1092-1, form D (instead of sealing surface B1, only for wetted parts made of stainless steel 316L)	M54
Sealing surface RF (groove) according to ASME B16.5 (instead of sealing surface RF 125 ... 250AA, only for wetted parts made of stainless steel 316L)	M64
Sealing surface with tongue to EN 1092-1, form C (for wetted parts made of stainless steel 316L only)	
• DN 40	M71
• DN 50	M72
• DN 80	M73
• DN 100	M74

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Level

Selection and ordering data (continued)

Options Add "Z" to article number, specify order code and plain text or entry from drop-down list.	Order code
• DN 125 Sealing surface with spigot according to EN 1092-1, form E (for wetted parts made of stainless steel 316L only)	M75
• DN 40 • DN 50 • DN 80 • DN 100 • DN 125 Sealing surface internal face according to EN 1092-1, form F (only for wetted parts made of stainless steel 316L)	M77 M78 M79 M80 M81 M84 M85 M86 M87
Remote seal connection Elongated pipe, 150 mm (5.9 inches) instead of 100 mm (3.9 inches) Elongated pipe, 200 mm (7.9 inches) instead of 100 mm (3.9 inches)	S05 S06
Desired remote seal supplier <u>Note:</u> If the remote seal is to be supplied only by one of the suppliers specified below, this option needs to be selected. For orders without this option, the remote seal supplier is selected through the dispatch center. Company WIKA, Klingenberg Company Labom, Hude	W01 W02
Special design Welded filling hole	X01
Customer-specific tube length Customer-specific tube length (specify in plain text in mm)	Y44
Specification of process conditions¹⁾ Ambient temperature range • -10 ... +50 °C (14 ... +122 °F) preset • -40 ... +50 °C (-40 ... +122 °F) • -10 ... +85 °C (14 ... +185 °F) Process temperature min. ... °C/°F/max. ... °C/°F	D66 D67 D68 Y50

¹⁾ See also "Specification of process conditions for selection and ordering data" below the "More information" section.

Technical specifications

SITRANS P320 / SITRANS P420 for level

Input

Measured variable

Measuring span (continuously adjustable) or measuring range and max. permissible operating pressure (pursuant to Pressure Equipment Directive 2014/68/EU)

Level

Measuring span

25 ... 250 mbar
2.5 ... 25 kPa
10 ... 100.5 inH₂O
25 ... 600 mbar
2.5 ... 60 kPa
10 ... 241 inH₂O
53 ... 1 600 mbar
5.3 ... 160 kPa
21 ... 643 inH₂O
166 ... 5 000 mbar
16.6 ... 500 kPa
2.41 ... 72.5 psi

Max. permissible operating pressure MAWP (PS)

Maximum permissible test pressure

See "Mounting flange"

Measuring limits

- Lower measuring limit

- Measuring cell with silicone oil filling
- Measuring cell with inert oil

- Measuring cell with FDA-compliant oil

- Upper measuring limit

- Lower range value

100% of max. measuring span

Between the measuring limits (continuously adjustable)

Output

Output signal

- Lower saturation limit (continuously adjustable)
- Upper saturation limit (continuously adjustable)
- Ripple (without HART communication)

HART

4 ... 20 mA

3.55 mA, factory set to 3.8 mA

22.8 mA, factory-set to 20.5 mA or optionally 22.0 mA

$I_{pp} \leq 0.5\%$ of max. output current

Adjustable damping

0 ... 100 s, continuously adjustable over remote operation

0 ... 100 s, in increments of 0.1 s, adjustable over display

- Current simulator

3.55 ... 22.8 mA

- Failure signal

3.55 ... 22.8 mA

Load

- Without HART communication

Resistance R [Ω]

$R = (U_H - 10.5 \text{ V}) / 22.8 \text{ mA}$,
 U_H : Auxiliary power in V

- With HART communication

$R = 230 \dots 1100 \Omega$

Characteristic curve

- Linearly increasing or linearly decreasing

- Linear increase or decrease or according to the square root (only for differential pressure and flow)

Physical bus

-

Polarity-independent

-

Measuring accuracy

Reference conditions

- According to IEC 62828-1
- Rising characteristic curve
- Lower range value 0 bar/kPa/psi
- Seal diaphragm stainless steel
- Measuring cell with silicone oil filling
- Room temperature 25 °C (77 °F)

Conformity error at limit point setting, including hysteresis and repeatability

Measuring span ratio r (spread, Turn-Down)

- Linear characteristic curve

$r = \text{maximum measuring span}/\text{set measuring span or nominal measuring range}$

$r \leq 5:$

$\leq 0.125\%$

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Level

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for level

- 250 mbar/25 kPa/3.6 psi	$5 < r \leq 10:$	$\leq (0.007 \cdot r + 0.09)\%$
- 600 mbar/60 kPa/8.7 psi		
- 1600 mbar/160 kPa/23.21 psi		
- 5 bar/500 kPa/72.5 psi		
Influence of ambient temperature in % per 28°C (50°F)		
• SITRANS P320	$\leq (0.025 \cdot r + 0.125)\%$	
- 250 mbar/25 kPa/3.6 psi		
- 600 mbar/60 kPa/8.7 psi		
- 1600 mbar/160 kPa/23.21 psi		
- 5 bar/500 kPa/72.5 psi		
• SITRANS P420	$\leq (0.025 \cdot r + 0.0625)\%$	
- 250 mbar/25 kPa/3.6 psi		
- 5 bar/500 kPa/72.5 psi		
- 600 mbar/60 kPa/8.7 psi	$\leq (0.125 \cdot r + 0.0625)\%$	
- 1600 mbar/160 kPa/23.21 psi		
Effect of static pressure		
• At the lower range value		
- 250 mbar/25 kPa/3.63 psi	$\leq (0.3 \cdot r)\%$ per nominal pressure	
- 600 mbar/60 kPa/8.7 psi	$\leq (0.15 \cdot r)\%$ per nominal pressure	
1.6 bar/160 kPa/23.21 psi		
5 bar/500 kPa/72.52 psi		
• On the measuring span	$\leq (0.1 \cdot r)\%$ per nominal pressure	
Long-term stability at $\pm 30^{\circ}\text{C}$ ($\pm 54^{\circ}\text{F}$)		
• All measuring cells	In 5 years $\leq (0.25 \cdot r)\%$ static pressure max. 70 bar/7 MPa/1015 psi	
Step response time T_{63} (without electrical damping)	Depends on the installed remote seal	
Influence of mounting position	Depends on the filling liquid in the mounting flange	
Effect of auxiliary power (in % per voltage change)	0.005% per 1 V	

Operating conditions

Medium temperature	
Measuring cell with silicone oil filling	<ul style="list-style-type: none"> High side: See "Mounting flange" Low side: -40 ... +100 °C (-40 ... +212 °F)
Ambient conditions	
• Ambient temperature/enclosure	Always consider the assignment of max. permissible operating temperature to max. permissible operating pressure of the respective flange connection.
- Measuring cell with silicone oil filling	-40 ... +85 °C (-40 ... +185 °F)
- Display	-20 ... +80 °C (-4 ... +176 °F)
• Storage temperature	-50 ... +85 °C (-58 ... +185 °F)
• Climatic class in accordance with IEC 60721-3-4	4K4H
• Degree of protection	IP66, IP68
- According to IEC 60529	Type 4X
- According to NEMA 250	
• Electromagnetic compatibility	
- Emitted interference and interference immunity	According to IEC 61326 and NAMUR NE 21

Structural design

Weight	Pressure transmitter with mounting flange, without tube
• According to EN	<ul style="list-style-type: none"> Aluminum enclosure: Approx. 11 ... 13 kg (24.2 ... 28.7 lbs) Stainless steel enclosure: Approx. 13 ... 15 kg (28.7 ... 33 lbs)
• According to ASME	<ul style="list-style-type: none"> Aluminum enclosure: Approx. 11 ... 18 kg (24.2 ... 39.7 lbs) Stainless steel enclosure: Approx. 13 ... 20 kg (28.7 ... 44 lbs)
Material	
• Material of wetted parts	

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for level

- High side	Seal diaphragm of mounting flange	Stainless steel, mat. no. 1.4404/316L, Monel 400, mat. no. 2.4360, Alloy B2, mat. no. 2.4617, Alloy C276, mat. no. 2.4819, Alloy C22, mat. no. 2.4602, tantalum, PTFE, PFA, ECTFE
- Gasket material in the process flanges	Sealing surface For standard applications For negative pressure applications on the mounting flange	Smooth according to EN 1092-1, form B1 or ASME B16.5 RF 125 ... 250 AA for stainless steel 316L, EN 2092-1 form B2 or ASME B16.5 RFSF for the remaining materials Viton Copper
- Low side	Seal diaphragm Process flanges Process flange screw O-ring	Stainless steel, mat. no. 1.4404/316L Stainless steel, mat. no. 1.4408/316 Stainless steel ISO 3506-1 A4-70 FPM (Viton)
• Material of non-wetted parts	<ul style="list-style-type: none"> - Electronics enclosure • Low-copper die-cast aluminum GD-AlSi 12 or stainless steel precision casting, mat. no. 1.4409/ CF-3M • Standard: Powder coating with polyurethane Option: 2 coats: Coat 1: Epoxy-based; coat 2: Polyurethane • Stainless steel nameplate (1.4404/316L) 	
Process flange screws	Stainless steel ISO 3506-1 A4-70	
Measuring cell filling	Silicone oil	
• Mounting flange filling liquid	Silicone oil or other material	
Process connection	Flange according to EN and ASME 1/4-18 NPT female thread and flange connection with M10 fastening thread according to DIN 19213 (M12 for PN 420 (MWP 6092 psi)) or 7/16-20 UNF according to EN 61518	
• High side		
• Low side		
Electrical connection	Screw terminals Cable entry via the following screw glands: <ul style="list-style-type: none"> • M20 x 1.5 • 1/2-14 NPT • Device plug Han 7D/Han 8D¹⁾ • Device plug M12 	
Displays and controls		
Buttons	4 buttons for operation directly on the device	
Display	<ul style="list-style-type: none"> • With or without integrated display (optional) • Lid with inspection window (optional) 	
Auxiliary power U_H		
Terminal voltage on pressure transmitter	10.5 ... 45 V DC 10.5 ... 30 V DC in intrinsically safe mode	
Ripple	$U_{SS} \leq 0.2 \text{ V}$ (47 ... 125 Hz)	
Noise	$U_{eff} \leq 1.2 \text{ mV}$ (0.5 ... 10 kHz)	
Auxiliary power	-	
Separate supply voltage	-	
Certificates and approvals		
Classification according to pressure equipment directive (PED 2014/68/EU)	For gases of fluid group 1 and liquids of fluid group 1; complies with requirements of article 4, paragraph 3 (sound engineering practice)	
Drinking water		
• WRAS (England)	No.: 1903094 (option E83)	
• ACS (France)	No.: 18 ACC LY 277 (option E85)	
• NSF (USA)	No.: 20180920-MH61350 (option E84)	
CRN (Canada)	No.: OF9863.5C (option E60)	
Explosion protection acc. to NEPSI (China)	No.: GYJ19.1058X (option E27)	
Explosion protection acc. to INMETRO (Brazil)	No.: BRA-18-GE-0035X (option E25)	
Explosion protection		
• Intrinsic safety "i"		
- Marking	II 1/2 G Ex ia/b IIC T4/T6 Ga/Gb	

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Level

Technical specifications (continued)

SITRANS P320 / SITRANS P420 for level

- Permissible ambient temperature	-40 ... +80 °C (-40 ... +176 °F) temperature class T4
- Permissible medium temperature	-40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Connection	To certified intrinsically safe circuits with peak values: $U_i = 30 \text{ V}$, $I_i = 101 \text{ mA}$, $P_i = 760 \text{ mW}$ $U_i = 29 \text{ V}$, $I_i = 110 \text{ mA}$, $P_i = 800 \text{ mW}$ $L_i = 0.24 \mu\text{H}$ / $C_i = 3.29 \text{ nF}$
- Effective internal inductance/capacitance	
• Flameproof enclosure "d"	Ex II 1/2 G Ex ia/db IIC T4/T6 Ga/Gb
- Marking	-40 ... +80 °C (-40 ... +176 °F) temperature class T4
- Permissible ambient temperature	-40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Permissible medium temperature	-40 ... +100 °C (-40 ... +212 °F) temperature class T4
- Connection	-40 ... +70 °C (-40 ... +158 °F) temperature class T6
• Dust explosion protection for Zones 20, 21, 22	To a circuit with the operating values: $U_n = 10.5 \dots 45 \text{ V}$, $4 \dots 20 \text{ mA}$
- Marking	
- Permissible ambient temperature	Ex II 1D Ex tb IIIC T120 °C Da
- Permissible medium temperature	Ex II 2D Ex tb IIIC T120 °C Db
- Max. surface temperature	Ex II 3D Ex tc IIIC T120 °C Dc
- Connection	-40 ... +80 °C (-40 ... +176 °F)
• Dust explosion protection for Zones 21, 22	-40 ... +100 °C (-40 ... +212 °F)
- Marking	120 °C (248 °F)
- Permissible ambient temperature	To a circuit with the operating values: $U_n = 10.5 \dots 45 \text{ V}$, $4 \dots 20 \text{ mA}$
- Permissible medium temperature	
- Connection	Ex II 2D Ex ib IIIC T120 °C Db
- Effective internal inductance/capacitance	-40 ... +80 °C (-40 ... +176 °F)
• Type of protection for Zone 2	-40 ... +100 °C (-40 ... +212 °F)
- Marking	To certified intrinsically safe circuits with peak values: $U_i = 30 \text{ V}$, $I_i = 101 \text{ mA}$, $P_i = 760 \text{ mW}$ $U_i = 29 \text{ V}$, $I_i = 110 \text{ mA}$, $P_i = 800 \text{ mW}$ $L_i = 0.24 \mu\text{H}$ / $C_i = 3.29 \text{ nF}$
- Permissible ambient temperature "ec"	
- Permissible medium temperature	Ex II 3G Ex ec IIC T4/T6 Gc
- "ec" connection	-40 ... +80 °C (-40 ... +176 °F) temperature class T4
• Explosion protection acc. to FM	-40 ... +40 °C (-40 ... +104 °F) temperature class T6
- Marking (XP/DIP) or IS; NI; S	-40 ... +100 °C (-40 ... +212 °F) temperature class T4
• Explosion protection according to CSA	-40 ... +70 °C (-40 ... +158 °F) temperature class T6
- Marking (XP/DIP) or (IS)	To a circuit with the operating values: $U_n = 10.5 \dots 30 \text{ V}$, $4 \dots 20 \text{ mA}$
NAMUR recommendations	Available soon
• NE 06	CL I, DIV 1, GP ABCD T4 ... T6; CL II, DIV 1, GP EFG; CL III; Ex ia IIC T4 ... T6: CL I, DIV 2, GP ABCD T4 ... T6; CL II, DIV 2, GP FG; CL III
• NE 21	Available soon
• NE 23	CL I, DIV 1, GP ABCD T4 ... T6; CL II, DIV 1, GP EFG; CL III; Ex ia IIC T4 ... T6: CL I, DIV 2, GP ABCD T4 ... T6; CL II, DIV 2, GP FG; CL III
• NE 43	Standardized Electrical Signals and Questions Relating to Engineering Technology
• NE 53	Electromagnetic Compatibility (EMC) of Industrial Process and Laboratory Control Equipment
• NE 80	Extra Low Voltage Circuits with Safe Separation
• NE 105	Standardization of the Signal Level for the Failure Information of Digital Transmitters
• NE 107	Software and Hardware of Field Devices and Signal Processing Devices with Digital Electronics
• NE 131	The Application of the Pressure Equipment Directive to Process Control Devices
	Specifications for Integrating Fieldbus Devices in Engineering Tools for Field Devices
	Self-Monitoring and Diagnosis of Field Devices
	NAMUR Standard Device - Field Devices for Standard Applications

¹⁾ Han 8D is identical to Han 8U.

Technical specifications (continued)

Mounting flange	
Nominal diameter	Nominal pressure
• According to EN 1092-1	
- DN 80	PN 40
- DN100	PN 16, PN 40
• According to ASME B16.5	
- 3 inches	Class 150, Class 300
- 4 inches	Class 150, Class 300

Communication	
HART	
HART	230 ... 1 100 Ω
Protocol	HART 7
Software for computer	SIMATIC PDM
PROFIBUS PA	
Simultaneous communication with master class 2 (max.)	4
The address can be set using	Configuration tool or local operation (default setting address 126)
Cyclic data usage	
• Output byte	≤ 35 (7 measured values)
• Input byte	0, 1, or 2 (register operation mode and reset function for dosing)
Internal preprocessing	
Device profile	PROFIBUS PA Profile Version 4.01 Class B. Cyclic data usage compatible with version 3.XX
Number of function blocks	
• Analog input	7
- Adaptation to user-specific process variable	Yes, linearly rising or falling characteristic curve
- Electrical damping adjustable	0 ... 100 s
- Simulation function	Output/input
- Limit monitoring	Yes, one upper and lower warning limit and one alarm limit respectively
• Register (totalizer)	Can be reset, preset, optional direction of counting, simulation function of register output
- Limit monitoring	One upper and lower warning limit and one alarm limit respectively
• Physical block	1
Transducer blocks	
• Pressure transducer block	1
- Can be calibrated by applying two pressures	Yes
- Monitoring of sensor limits	Yes
- Specification of a vessel characteristic curve with	Max. 30 nodes
- Square-rooted characteristic curve for flow measurement	Yes
- Tank characteristic curve for volume measurement	Yes
- Low flow cut-off and implementation point of square-root extraction	Parameterizable
- Simulation function for measured pressure value and sensor temperature	Constant value or by means of parameterizable ramp function
FOUNDATION Fieldbus	
Device profile	FF ITK 6
Function blocks	3 function blocks analog input, 1 function block PID

Pressure measurement


Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Level

Technical specifications (continued)

Communication	
• Analog input	
- Adaptation to user-specific process variable	Yes, linearly rising or falling characteristic curve
- Electrical damping adjustable	0 ... 100 s
- Simulation function	Output/input (can be locked within the device with a bridge)
- Failure mode	Parameterizable (last good value, substitute value, incorrect value)
- Limit monitoring	Yes, one upper and lower warning limit and one alarm limit respectively
- Square-rooted characteristic curve for flow measurement	Yes
• PID	Standard FOUNDATION Fieldbus function block
• Physical block	1 resource block
Transducer blocks	1 transducer block Pressure with calibration, 1 transducer block LCD
• Pressure transducer block	
- Can be calibrated by applying two pressures	Yes
- Monitoring of sensor limits	Yes
- Simulation function: pressure measurement, sensor temperature and electronics temperature	Constant value or by means of parameterizable ramp function

Dimensional drawings



SITRANS P320/P420 pressure transmitter for level, including mounting flange, dimensions in mm (inch)

Connection to EN 1092-1

Nominal diameter	Nominal pressure	b	D	d ₂	d ₄	d ₅	d _M with tube	d _M Without tube	f	k	n	L
		mm	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm
DN 40	PN 10/16/25/40	16	150	18	88	38	30	42	2	110	4	0, 50, 100, 150 or 200
	PN 63/100	24	170	22	88	38	30	42	2	125	4	
	PN 160	26	170	22	88	38	30	42	2	125	4	
DN 50	PN 10/16/25/40	18	165	18	102	48.3	40	51	2	125	4	
	PN 63/100	26	195	26	102	48.3	40	51	2	145	4	
	PN 160	28	195	26	102	48.3	40	51	2	145	4	
DN 80	PN 10/16/25/40	22	200	18	138	76	65	85	2	160	8	
	PN 100	30	230	26	138	76	65	85	2	180	8	

Pressure measurement

Pressure transmitters

for applications with advanced requirements / SITRANS P320/420 / Level

Dimensional drawings (continued)

Nominal diameter	Nominal pressure	b	D	d ₂	d ₄	d ₅	d _M with tube	d _M Without tube	f	k	n	L
		mm	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm
DN 100	PN 10/16	18	220	18	158	94	85	85	2	180	8	0, 50, 100, 150 or 200
	PN 25/40	22	235	22	162	94	85	85	2	190	8	
DN 125	PN 16	20	250	18	188	127	85	116	2	210	8	
	PN 40	24	270	26	188	127	85	116	2	220	8	

Connection according to ASME B16.5

Nominal diameter	Nominal pressure	b	D	d ₂	d ₄	d ₅	d _M with tube	d _M Without tube	f	k	n	L
		lb/sq.in.	Inch (mm)	Inch (mm)	Inch (mm)	Inch (mm)	Inch (mm)	Inch (mm)	Inch (mm)	Inch (mm)	Inch (mm)	Inch (mm)
1½ inches	150	0.63 (15.9)	4.92 (125)	0.63 (15.9)	2.87 (73)	1.5 (38)	1.18 (30)	1.42 (36)	0.08 (2)	3.87 (98.4)	4	0, 2, 3.94,
	300	0.75 (19.1)	6.10 (155)	0.87 (22.2)	2.87 (73)	1.5 (38)	1.18 (30)	1.42 (36)	0.08 (2)	4.5 (114.3)	4	5.94 or
	400/600	0.88 (22.3)	6.10 (155)	0.87 (22.2)	2.87 (73)	1.5 (38)	1.18 (30)	1.42 (36)	0.28 (7)	4.5 (114.3)	4	7.87
	900/1500	1.25 (31.8)	7.09 (180)	1.13 (28.6)	2.87 (73)	1.5 (38)	1.18 (30)	1.42 (36)	0.28 (7)	4.87 (123.8)	4	(0, 50, 100, 150 or 200)
2 inches	150	0.69 (17.5)	5.91 (150)	0.75 (19.1)	3.63 (92.1)	1.9 (48.3)	1.57 (40)	2.01 (51)	0.08 (2)	4.75 (120.7)	4	
	300	0.81 (20.7)	6.5 (165)	0.75 (19.1)	3.63 (92.1)	1.9 (48.3)	1.57 (40)	2.01 (51)	0.08 (2)	5 (127)	8	
	400/600	1.00 (25.4)	6.5 (165)	0.75 (19.1)	3.63 (92.1)	1.9 (48.3)	1.57 (40)	2.01 (51)	0.28 (7)	5 (127)	8	
	900/1500	1.5 (38.1)	8.46 (215)	1.00 (25.4)	3.63 (92.1)	1.9 (48.3)	1.57 (40)	2.01 (51)	0.28 (7)	6.5 (165.1)	8	
3 inches	150	0.88 (22.3)	7.48 (190)	0.75 (19.1)	5 (127)	3 (76)	2.65 (65)	3.35 (85)	0.08 (2)	6 (152.4)	4	
	300	1.06 (27)	8.27 (210)	0.87 (22.2)	5 (127)	3 (76)	2.65 (65)	3.35 (85)	0.08 (2)	6.63 (168.3)	8	
	600	1.23 (31.8)	8.27 (210)	0.87 (22.2)	5 (127)	3 (76)	2.65 (65)	3.35 (85)	0.28 (7)	6.63 (168.3)	8	
	1500	1.88 (47.7)	10.43 (265)	1.25 (31.8)	5 (127)	3 (76)	2.65 (65)	3.35 (85)	0.28 (7)	8 (203.2)	8	
4 inches	150	0.88 (22.3)	9.06 (230)	0.75 (19.1)	6.19 (157.2)	3.69 (94)	3.35 (85)	3.35 (85)	0.08 (2)	7.5 (190.5)	8	
	300	1.19 (30.2)	10.04 (255)	0.87 (22.2)	6.19 (157.2)	3.69 (94)	3.35 (85)	3.35 (85)	0.08 (2)	7.87 (200)	8	
	400	1.38 (35)	10.04 (255)	0.87 (22.2)	6.19 (157.2)	3.69 (94)	3.35 (85)	3.35 (85)	0.28 (7)	7.87 (200)	8	
	1500	2.13 (54)	12.20 (310)	1.37 (34.9)	6.19 (157.2)	3.69 (94)	3.35 (85)	3.35 (85)	0.28 (7)	9.5 (241.3)	8	
5 inches	150	0.88 (22.3)	10.04 (255)	0.87 (22.2)	7.31 (185.7)	5 (127)	4.57 (116)	4.57 (116)	0.08 (2)	8.5 (215.9)	8	
	300	1.31 (33.4)	11.02 (280)	0.87 (22.2)	7.31 (185.7)	5 (127)	4.57 (116)	4.57 (116)	0.08 (2)	9.25 (235)	8	
	400	1.50 (38.1)	11.02 (280)	0.87 (22.2)	7.31 (185.7)	5 (127)	4.57 (116)	4.57 (116)	0.28 (7)	9.25 (235)	8	

Process connection according to J.I.S

Nominal diameter	Nominal pressure	b	D	d ₂	d ₄	d ₅	d _M with tube	d _M Without tube	f	k	n	L
		mm (inch)	mm (inch)	mm (inch)	mm (inch)	mm (inch)	mm (inch)	mm (inch)	mm (inch)	mm (inch)	mm (inch)	mm (inch)
DN 50	10 K	14 (0.55)	155 (6.10)	19 (0.75)	96 (3.78)	48.3 (1.9)	40 (1.57)	51 (2.01)	2	120 (4.72)	4	0, 50, 100, 150 or 200
	20 K	16 (0.63)	165 (6.50)	19 (0.75)	96 (3.78)	48.3 (1.9)	40 (1.57)	51 (2.01)	2	120 (4.72)	8	(0, 2, 3.94,
	40 K	26 (1.02)	165 (6.50)	19 (0.75)	105 (4.13)	48.3 (1.9)	40 (1.57)	51 (2.01)	2	130 (5.12)	8	5.94 or 7.87)
DN 80	10 K	16 (0.63)	185 (7.28)	19 (0.75)	126 (4.96)	76 (2.99)	65 (2.56)	85 (3.35)	2	150 (5.91)	8	
	20 K	20 (0.79)	200 (7.87)	23 (0.91)	132 (5.20)	76 (2.99)	65 (2.56)	85 (3.35)	2	160 (6.30)	8	
	40 K	32 (1.26)	210 (8.27)	23 (0.91)	140 (5.51)	76 (2.99)	65 (2.56)	85 (3.35)	2	170 (6.30)	8	
DN 100	10 K	16 (0.63)	210 (8.27)	19 (0.75)	151 (5.94)	94 (3.7)	85 (3.35)	85 (3.35)	2	175 (6.89)	8	
	20 K	22 (0.87)	225 (8.86)	23 (0.91)	160 (6.30)	94 (3.7)	85 (3.35)	85 (3.35)	2	185 (7.28)	8	
	40 K	36 (1.42)	250 (9.84)	25 (0.98)	165 (6.50)	94 (3.7)	85 (3.35)	85 (3.35)	2	205 (8.07)	8	

d: Inside diameter of gasket according to DIN 2690

d_M: Effective diaphragm diameter

More information

Specification of process conditions for selection and ordering data

Ambient temperature range

The standard remote seal systems are optimized for an ambient temperature range of -10 to +50 °C (14 to +122 °F). Therefore, in the ordering options, the **order code "D66"** is preset.

If the range of the ambient temperature deviates from this, you have the possibility to choose other ambient temperature ranges:

- With the **order code D67**, a range from -40 to +50 °C (-40 to +122 °F)
- With the **order code D68**, a range from -10 to +85 °C (14 to +185 °F)

In the case of a **special design**, which you can select with the **order option Y99** in the device settings, it is possible to enter the ambient temperature as a numerical value.

Process temperature

The standard optimization for the process temperature depends on the filling liquid used:

Filling liquid	Code	Optimized temperature range as standard
Silicone M50	B	-10 ... +200 °C (14 ... +392 °F)
High-temperature oil	C	-10 ... +300 °C (14 ... +572 °F)
Silicone oil M5	A	-40 ... +140 °C (-40 ... +284 °F)
Food oil (FDA-listed)	E	-10 ... +140 °C (14 ... +284 °F)
Halocarbon oil	D	-20 ... +60 °C (-4 ... +140 °F)
Neobee M20 (FDA-listed)	R	-10 ... +140 °C (14 ... +284 °F)

- If the process temperatures deviate from the temperature ranges mentioned in the table above, we ask you to send the process temperature with the **order code Y50** along with the order.
- If the remote seal has a small diameter (< DN 50/2") or a long capillary (> 4 m), we also ask you to provide the process data with the **following order code** when ordering.

These entries are transmitted and ensure the correct functioning of the remote seal systems.

Order code	
Ambient temperature range	
• -10 ... +50 °C (14 ... +122 °F) preset	D66
• -40 ... +50 °C (-40 ... +122 °F)	D67
• -10 ... +85 °C (14 ... +185 °F)	D68
Process temperature min. ... °C/°F/max. ... °C/°F	Y50