

# NRAG7.E239877 - PROGRAMMABLE CONTROLLERS FOR USE IN HAZARDOUS LOCATIONS CERTIFIED FOR CANADA

## Programmable Controllers for Use in Hazardous Locations Certified for Canada

See General Information for Programmable Controllers for Use in Hazardous Locations Certified for Canada

### SIEMENS AG

E239877

Breslauer Strasse 5  
90766 Fuerth, GERMANY

**Class I, Division 2, Groups A, B, C and D, communication processors, "SIPLUS System NET",** Model(s) 6AG1343-1CX10-4XE0

**Class I, Division 2, Groups A, B, C and D, CPU modules,** Model(s) 6AG1195-7HD10-4XA0, 6AG1312-5BD00-2AB0, 6AG1312-5BD01-2AB0, 6AG1312-5BE03-2AB0, 6AG1313-5BE00-2AB0, 6AG1313-5BE01-2AB0, 6AG1313-5BF03-2AB0, 6AG1313-6CF03-2AB0, 6AG1314-1AF10-2AB0, 6AG1314-1AG13-2AB0, 6AG1314-1AG14-7AB0, 6AG1314-6BG03-7AB0, 6AG1314-6CG03-2AB0, 6AG1315-2AG10-2AB0, 6AG1315-2AH14-7AB0, 6AG1315-2EH13-2AB0, 6AG1315-2FH13-2AB0, 6AG1315-6FF04-2AB0, 6AG1317-2EK13-2AB0, 6AG1317-2FK13-2AB0, 6AG1331-7NF00-2AB0, 6AG1332-5HF00-2AB0, 6AG1417-4HL04-4AB0, 6AG1443-1EX11-4XE0, 6AG1960-1AA04-4XA0

**Class I, Division 2, Groups A, B, C and D, front panel mounted panel series, "SIMATIC HMI",** Model(s) 6AV2144-8QC10-0AA1, 6AV2144-8UC10-0AA1

**Class I, Division 2, Groups A, B, C and D, Front panel mounted panel series Simatic HMI, "TP1200 Comfort INOX PCT",** Model(s) 6AV2144-8MC20-0AA0

**Class I, Division 2, Groups A, B, C and D, Front panel mounted panel series Simatic HMI, "TP700 Comfort INOX PCT",** Model(s) 6AV2144-8GC20-0AA0

**Class I, Division 2, Groups A, B, C and D, Front panel mounted panel series Simatic HMI, "TP900 Comfort INOX PCT",** Model(s) 6AV2144-8JC20-0AA0

**Class I, Division 2, Groups A, B, C and D, function-devices,** Model(s) 6AG1350-1AH03-2AE0, 6AG1350-2AH01-4AE0

**Class I, Division 2, Groups A, B, C and D, I/O devices,** Model(s) 6AG1321-1FF10-7AA0, 6AG1321-7TH00-4AB0, 6AG1322-5FF00-4AB0, 6AG1322-5HF00-4AB0, 6AG1322-8BH01-2AB0, 6AG1326-1RF00-4AB0, 6AG1326-2BF40-2AB0, 6AG1331-7TF01-4AB0, 6AG1331-7TF01-7AB0, 6AG1332-7ND02-4AB0, 6AG1332-8TF01-2AB0, 6AG1332-8TF01-4AB0, 6AG1336-4GE00-4AB0, 6AG1341-1CH02-7AE0

**Class I, Division 2, Groups A, B, C and D, I/O modules,** Model(s) 6AG1195-7HB00-4XA0, 6AG1195-7HD10-4XA0, 6AG1322-1BF01-2XB0, 6AG1331-1KF01-4AB0, 6AG1331-7KF02-2AB0, 6AG1331-7NF00-2AB0, 6AG1332-5HF00-2AB0, 6AG1340-1AH02-2AE0

**Class I, Division 2, Groups A, B, C and D, IPLUS system S7-1200,** Model(s) 6AG1243-1JX30-7XE0

**Class I, Division 2, Groups A, B, C and D, mounting racks,** Model(s) 6AG1400-2JA10-4AA0

**Class I, Division 2, Groups A, B, C and D, NRAG, "SIMATIC System ET200SP",** Model(s) 6AG1131-6BF01-7BA0, 6AG1131-6BF61-7AA0, 6AG1131-6BH01-7BA0, 6AG1131-6FD01-7BB1, 6AG1132-6BF01-7BA0, 6AG1132-6BF61-7AA0, 6AG1132-6BH01-7BA0, 6AG1132-6GD51-2BA0, 6AG1132-6HD01-7BB1, 6AG1134-6PA20-7BD0, 6AG1151-1AA06-7AB0, 6AG1155-6AU01-7BN0

**Class I, Division 2, Groups A, B, C and D, Open type, programmable controllers, "SIMATIC System ET200M",** Model(s) 6AG1155-5AA01-7AB0, 6AG1336-4GE00-2AB0, 6AG1411-5AB10-2AA0

**Class I, Division 2, Groups A, B, C and D, Open type, programmable controllers, "SIMATIC System ET200SP",** Model(s) 6AG1131-6CF00-7AU0, 6AG1136-6AA00-2CA1, 6AG1155-6AU01-2CN0, 6AG1155-6BU01-7CN0, 6AG1677-2DB40-2AA0

**Class I, Division 2, Groups A, B, C and D, Open type, programmable controllers, "SIPLUS system LOGO!",** Model(s) 6AG1052-1CC08-7BA0, 6AG1052-1FB08-7BA0, 6AG1052-1HB08-7BA0, 6AG1052-1MD08-7BA0, 6AG1052-2CC08-7BA0, 6AG1052-2FB08-7BA0, 6AG1052-2HB08-7BA0, 6AG1052-2MD08-7BA0, 6AG1055-1MD00-7BA2, 6AG1055-4MH08-2BA0

**Class I, Division 2, Groups A, B, C and D, Open type, programmable controllers, "SIPLUS System S7-1500/ET 200MP",** Model(s) 6AG1511-1AK02-2AB0, 6AG1511-1AK02-7AB0, 6AG1511-1FK02-2AB0, 6AG1513-1AL02-2AB0, 6AG1513-1AL02-7AB0, 6AG1513-1FL02-2AB0, 6AG1515-2FM01-2AB0, 6AG1515-2RM00-7AB0, 6AG1518-4AX00-4AB0, 6AG1526-1BH00-2AB0, 6AG1526-2BF00-2AB0

**Class I, Division 2, Groups A, B, C and D, Open type, programmable controllers, "SIPLUS System, SIMATIC System ET200SP",** Model(s) 6AG1132-6FD00-7CU0, 6AG1132-6GD51-7BA0, 6AG1134-6GD01-2BA1, 6AG1134-6GD01-7BA1, 6AG1134-6GF00-7AA1, 6AG1134-6HD01-2BA1, 6AG1134-6HD01-7BA1, 6AG1135-6HB00-7CA1, 6AG1136-6DC00-2CA0, 6AG1155-6AU01-7CN0, 6AG1193-6BP00-7BU0, 6AG1193-6BP00-7DU0, 6AG1510-1DJ01-7AB0, 6AG1512-1DK01-7AB0

**Class I, Division 2, Groups A, B, C and D, Open type, programmable controllers, "SIPLUS WP321",** Model(s) 6AG1138-6AA00-2BA8

**Class I, Division 2, Groups A, B, C and D, Programmable controller, "SIMATIC",** Model(s) MP 277T-10 INOX Ex2 6AV6 643-0ED01-..., MP 377 15 Touch Daylight 6AV6 644-8AB20-..., MP 377 15 Touch INOX 6AV6 644-0CB01-..., TP 177B color INOX 6AV6 642-8BA10-....

**Class I, Division 2, Groups A, B, C and D, Programmable controllers, "SIMATIC System ET200SP",** Model(s) 6AG1131-6BF00-7CA0, 6AG1132-6BD20-7CA0, 6AG1138-6BA00-2BA0, 6AG1138-6CG00-2BA0, 6AG1155-6AU00-2CN0, 6AG1193-6AG00-2AA0, 6AG1677-2AA40-4AA0

**Class I, Division 2, Groups A, B, C and D, programmable controllers,** Model(s) 6AG1131-1BH01-2XB0, 6AG1131-4BD01-2AA0, 6AG1131-4BD01-7AB0, 6AG1131-4BF00-7AA0, 6AG1131-4BF50-7AA0, 6AG1132-4BB01-2AB0, 6AG1132-4BB31-7AB0, 6AG1132-4BD01-2AA0, 6AG1132-4BD02-7AA0, 6AG1132-4BD32-2AA0, 6AG1132-4BF00-7AA0, 6AG1132-4BF50-7AA0, 6AG1132-4HB01-2AB0, 6AG1132-4HB12-2AB0, 6AG1134-4FB01-2AB0, 6AG1134-4GB01-2AB0, 6AG1134-4GB11-2AB0, 6AG1134-4GB52-2AB0, 6AG1134-4GD00-2AB0, 6AG1134-4JB50-2AB0, 6AG1134-4JB51-7AB0, 6AG1134-4LB02-2AB0, 6AG1134-4MB02-2AB0, 6AG1134-4NB01-7AB0, 6AG1134-4NB51-2AB0, 6AG1134-6TD00-2CA1, 6AG1135-4FB01-2AB0, 6AG1135-4GB01-2AB0, 6AG1135-4LB02-7AB0, 6AG1138-4CA01-2AA0, 6AG1138-4CA50-2AB0, 6AG1138-4CB11-2AB0, 6AG1138-4DA04-2AB0, 6AG1138-4DD01-7AB0, 6AG1138-4DF01-7AB0, 6AG1138-4DF11-7AB0, 6AG1138-4FA03-2AB0, 6AG1138-4FA04-2AB0, 6AG1138-4FA05-2AB0, 6AG1138-4FB02-2AB0, 6AG1138-4FB03-2AB0, 6AG1138-4FB04-2AB0, 6AG1138-4HA00-7AB0, 6AG1151-1AA04-2AB0, 6AG1151-1AA05-7AB0, 6AG1151-1BA02-2AB0, 6AG1151-3AA22-2AB0, 6AG1151-3AA23-2AB0, 6AG1151-3BA23-7AB0, 6AG1151-7AA20-7AB0, 6AG1151-7FA01-2AB0, 6AG1151-7FA20-2AB0, 6AG1151-8AB01-7AB0, 6AG1151-8FB01-2AB0, 6AG1153-1AA03-2XB0, 6AG1153-2BA00-2XB0, 6AG1153-2BA02-2XY0, 6AG1153-2BA02-7XB0, 6AG1153-2BA10-7XB0, 6AG1153-4AA01-7XB0, 6AG1153-4BA00-7XB0, 6AG1155-5AA00-2AC0, 6AG1193-1CH00-2XA0, 6AG1193-4JA00-2AA0, 6AG1195-7HA00-2XA0, 6AG1195-7HB00-7XA0, 6AG1195-7HC00-2XA0, 6AG1195-7HD10-2XA0, 6AG1195-7HG00-2XA0, 6AG1195-7KF00-2XA0, 6AG1315-6FF01-2AB0, 6AG1317-6FF00-2AB0, 6AG1321-1BH02-2AA0, 6AG1321-1BL00-2AA0, 6AG1321-1CH20-2AA0, 6AG1321-1FF01-2AA0, 6AG1321-1FH00-7AA0, 6AG1321-7BH01-2AB0, 6AG1322-1BF01-4AA0, 6AG1322-1BH01-2AA0, 6AG1322-1BL00-2AA0, 6AG1322-1CF00-2AA0, 6AG1322-1CF00-7AA0, 6AG1322-1FF01-2AA0, 6AG1322-1FF01-7AA0, 6AG1322-1FH00-7AA0, 6AG1322-1HF10-2AA0, 6AG1322-1HH01-2AA0, 6AG1322-8BF00-2AB0, 6AG1323-1BH01-2AA0, 6AG1326-1BK00-2AB0, 6AG1326-1BK00-4AB0, 6AG1326-1BK02-2AB0, 6AG1326-2BF01-2AB0, 6AG1326-2BF01-4AB0, 6AG1326-2BF41-2AB0, 6AG1331-7KB02-2AB0, 6AG1331-7KF02-4AB0, 6AG1331-7PF00-4AB0, 6AG1331-7RD00-2AB0, 6AG1331-7SF00-4AB0, 6AG1331-7TB00-4AB0, 6AG1331-7TB00-7AB0, 6AG1332-5HB01-2AB0, 6AG1332-5HD01-4AB0, 6AG1332-5HD01-7AB0, 6AG1332-5HF00-4AB0, 6AG1334-0KE00-2AB0, 6AG1334-0KE00-7AB0, 6AG1341-1AH02-7AE0, 6AG1350-2AH00-4AE0, 6AG1353-2AA02-4XB0, 6AG1365-0BA01-2AA0, 6AG1545-0CC10-4AX0, 6AG1641-0CA01-4AX0, 6AG1643-0CD01-4AX0, 7MH4138-6AA00-0BA0, 7MH4900-2AA01, 7MH4900-3AA01, 7MH4910-0AA01, 7MH4920-0AA01, 7MH4930-0AA01, 7MH4950-1AA01, 7MH4950-2AA01, 7MH4980-1AA01, 7MH4980-2AA01

**Class I, Division 2, Groups A, B, C and D, Programmable Controllers for use in HazLoc,** Model(s) AI 2xSG 4-/6-wire HS, Cat No 7MH4134-6LB00-0DA0

**Class I, Division 2, Groups A, B, C and D, Simatic HMI comfort,** Model(s) 6AV2144-6JC10-0AL0, 6AV2144-6QC00-0AA0, 6AV2144-6QC10-0AL0, 6AV2144-6XC00-0AA0, 6AV2144-6XC10-0AL0, 6AV2144-8JC10-0AA0, 6AV2144-8JC10-0SL0, 6AV2144-8MC10-0AC0, 6AV2144-8QC10-0AA0, 6AV2144-8QC10-0SL0

**Class I, Division 2, Groups A, B, C and D, SIMATIC SIPLUS system S7-1500,** Model(s) 6AG1332-4BA00-7AA0, 6AG1333-4BA00-7AA0

**Class I, Division 2, Groups A, B, C and D, SIPLUS ET200S,** Model(s) 6AG1151-7AA21-2AB0, 6AG1151-7FA21-2AB0

**Class I, Division 2, Groups A, B, C and D, SIPLUS ET200SP,** Model(s) 6AG1131-6BF00-7BA0, 6AG1131-6BF60-7AA0, 6AG1131-6BH00-7BA0, 6AG1131-6FD00-7BB1, 6AG1131-6TF00-7CA0, 6AG1132-6BD20-7BA0, 6AG1132-6BF00-7BA0, 6AG1132-6BF00-7CA0, 6AG1132-6BF60-7AA0, 6AG1132-6BH00-7BA0, 6AG1132-6GD50-2BA0, 6AG1134-6FF00-2AA1, 6AG1134-6GD00-7BA1, 6AG1134-6HB00-2CA1, 6AG1134-6HB00-7BA1, 6AG1135-6HD00-7BA1, 6AG1134-6JD00-2CA1, 6AG1134-6JF00-2CA1, 6AG1134-6PA00-7BD0, 6AG1135-6GB00-7BA1, 6AG1135-6HB00-2DA1, 6AG1135-6HD00-7BA1, 6AG1136-6BA00-2CA0, 6AG1136-6DB00-2CA0, 6AG1136-6PA00-2BC0, 6AG1136-6RA00-2BF0, 6AG1137-6AA00-2BA0, 6AG1137-6BD00-2BA0, 6AG1138-6AA00-2BA0, 6AG1138-6DB00-2BB1, 6AG1155-6AU00-4CN0, 6AG1155-6AU00-7BN0, 6AG1155-6BU00-7CN0, 6AG1193-6AF00-7AA0, 6AG1193-6AP00-2AA0, 6AG1193-6AR00-7AA0, 6AG1193-6BP00-7BA0, 6AG1193-6BP00-7BA1, 6AG1193-6BP00-7BD0, 6AG1193-6BP00-7DA0, 6AG1193-6BP00-7DA1, 6AG1193-6BP20-2BF0, 6AG1193-6BP20-7BA0, 6AG1193-6BP20-7BB0, 6AG1193-6BP20-7BB1, 6AG1193-6BP20-7DA0, 6AG1193-6BP20-7DC0, 6AG1193-6BP40-7BA1, 6AG1193-6BP40-7DA1, 6AG1193-6PA00-7AA0, 6AG1510-1DJ00-2AB0, 6AG1510-1DJ01-2AB0, 6AG1510-1SJ01-2AB0, 6AG1512-1DK00-2AB0, 6AG1512-1DK01-2AB0, 6AG1512-1SK01-2AB0, 6AG1545-5DA00-2AB0

**Class I, Division 2, Groups A, B, C and D, SIPLUS NET CP 343-1/ SIPLUS S7-300,** Model(s) 6AG1340-1AH02-2AY0, 6AG1343-1EX30-4XE0, 6AG1343-1EX30-7XE0, 6AG1343-1GX30-4XE0 (CP 343-1 ERTEC Advanced)

**Class I, Division 2, Groups A, B, C and D, SIPLUS S7-300,** Model(s) 6AG1312-5BF04-2AY0, 6AG1312-5BF04-7AB0, 6AG1313-5BG04-2AY0, 6AG1313-5BG04-7AB0, 6AG1313-6CG04-2AY0, 6AG1313-6CG04-7AB0, 6AG1314-6BH04-7AB0, 6AG1314-6CH04-2AY0, 6AG1314-6CH04-7AB0, 6AG1314-6EH04-7AB0, 6AG1317-6FF04-2AB0, 6AG1326-2BF41-2AY0, 6AG1654-7HY00-7XA0

**Class I, Division 2, Groups A, B, C and D, SIPLUS S7-400,** Model(s) 6AG1400-1JA11-7AA0, 6AG1400-1TA11-7AA0, 6AG1400-2JA10-7AA0, 6AG1412-2EK06-2AB0, 6AG1412-5HK06-7AB0, 6AG1414-3EM06-7AB0, 6AG1414-5HM06-7AB0, 6AG1416-3ES06-7AB0, 6AG1416-5HS06-7AB0, 6AG1417-4HT14-4AB0, 6AG1417-5HT06-7AB0, 6AG1421-1BL01-2AA0, 6AG1422-1BL00-2AA0, 6AG1431-0HH00-4AB0, 6AG1432-1HF00-4AB0, 6AG1460-0AA01-2AB0, 6AG1461-0AA01-2AA0, 6AG1964-2AA04-7AB0

**Class I, Division 2, Groups A, B, C and D, SIPLUS system,** Model(s) 6AG1972-0BA12-2XA0, 6AG1972-0BA42-7XA0, 6AG1972-0BB12-2XA0, 6AG1972-0BB42-7XA0, 6AG1972-0BB70-7XA0, 6AG1972-0DA00-2AA0

**Class I, Division 2, Groups A, B, C and D, SIPLUS system HMI**, Model(s) 6AG1641-0AA11-4AX0, 6AG1641-0CA01-4AX1, 6AG1642-0BA01-4AX1, 6AG1642-0BC01-4AX1, 6AG1642-0BD01-2AX0, 6AG1642-0BD01-4AX0, 6AG1642-0DA01-4AX1, 6AG1642-0DC01-4AX1, 6AG1642-0EA01-4AX0, 6AG1643-0AA01-4AX0, 6AG1643-0BA01-4AX1, 6AG1643-0CD01-4AX1, 6AG1644-0AA01-4AX0, 6AG1644-0AB01-4AX0

**Class I, Division 2, Groups A, B, C and D, SIPLUS system HMI comfort**, Model(s) 6AG1124-0GC01-4AX0, 6AG1124-0GC13-2AX0, 6AG1124-0JC01-4AX0, 6AG1124-0MC01-4AX0, 6AG1124-0QC02-4AX0, 6AG1124-0UC02-4AX0, 6AG1124-0XC02-4AX0, 6AG1124-1DC01-4AX0, 6AG1124-1GC01-4AX0, 6AG1124-1JC01-4AX0, 6AG1124-1MC01-4AX0, 6AG1124-1QC02-4AX0, 6AG1124-2DC01-4AX0, 6AG1647-0AH11-2AX0, 6AG1688-3AY36-2AX0

**Class I, Division 2, Groups A, B, C and D, SIPLUS system LOGO!**, Model(s) 6AG1052-1CC01-2BA6, 6AG1052-1CC01-7BA8, 6AG1052-1FB00-2BA7, 6AG1052-1FB00-7BA8, 6AG1052-1HB00-7BA8, 6AG1052-1MD00-2BA7, 6AG1052-1MD00-7BA8, 6AG1052-2CC01-2BA6, 6AG1052-2CC01-7BA8, 6AG1052-2FB00-7BA8, 6AG1052-2HB00-7BA8, 6AG1052-2MD00-7BA8, 6AG1055-1CB00-7BA2, 6AG1055-1FB00-7BA2, 6AG1055-1HB00-7BA2, 6AG1055-1MA00-7BA2, 6AG1055-1MB00-7BA2, 6AG1055-1MM00-2BY1, 6AG1055-1MM00-7BA2, 6AG1055-1NB10-7BA2, 6AG1055-4MH00-2BA0, 6AG1055-4MH00-7BA1

**Class I, Division 2, Groups A, B, C and D, SIPLUS system NET**, Model(s) 6AG1342-5DA02-2XE0, 6AG1342-5DA02-4XE0, 6AG1343-1CX10-2XE0, 6AG1343-1EX21-4XE0, 6AG1343-1GX21-4XE0

**Class I, Division 2, Groups A, B, C and D, SIPLUS system S7**, Model(s) 6AG1322-8BH10-7AB0, 6AG1326-1RF01-4AB0, 6AG1370-0AA01-7AA0, 6AG1972-0AA02-7XA0, 6AG1972-0AB01-4XA0

**Class I, Division 2, Groups A, B, C and D, SIPLUS system S7-1500/ET 200MP**, Model(s) 6AG1155-5AA00-7AB0, 6AG1155-5BA00-2AB0, 6AG1505-0KA00-7AB0, 6AG1505-0RA00-7AB0, 6AG1507-0RA00-7AB0, 6AG1511-1AK00-2AB0, 6AG1511-1AK00-7AB0, 6AG1511-1AK01-2AB0, 6AG1511-1AK01-7AB0, 6AG1511-1FK01-2AB0, 6AG1513-1AL00-2AB0, 6AG1513-1AL00-7AB0, 6AG1513-1AL01-2AB0, 6AG1513-1AL01-7AB0, 6AG1513-1FL00-2AB0, 6AG1513-1FL01-2AB0, 6AG1516-3AN00-2AB0, 6AG1516-3AN00-7AB0, 6AG1516-3AN01-2AB0, 6AG1516-3AN01-7AB0, 6AG1516-3FN00-2AB0, 6AG1516-3FN01-2AB0, 6AG1518-4AP00-4AB0, 6AG1518-4FP00-4AB0, 6AG1521-1BH00-7AB0, 6AG1521-1BH50-7AA0, 6AG1521-1BL00-7AB0, 6AG1521-1FH00-7AA0, 6AG1521-7EH00-7AB0, 6AG1522-1BF00-7AB0, 6AG1522-1BH00-7AB0, 6AG1522-1BH01-7AB0, 6AG1522-1BL00-7AB0, 6AG1522-1BL01-7AB0, 6AG1522-5EH00-7AB0, 6AG1522-5FF00-7AB0, 6AG1522-5FH00-7AB0, 6AG1522-5HF00-2AB0, 6AG1522-5HH00-7AB0, 6AG1531-7KF00-7AB0, 6AG1531-7NF00-7AB0, 6AG1531-7NF10-7AB0, 6AG1531-7PF00-4AB0, 6AG1532-5HD00-7AB0, 6AG1532-5HF00-7AB0, 6AG1540-1AB00-7AA0, 6AG1540-1AD00-7AA0, 6AG1541-1AB00-7AB0, 6AG1541-1AD00-7AB0, 6AG1542-5DX00-7XE0, 6AG1550-1AA00-7AB0, 6AG1551-1AB00-7AB0

**Class I, Division 2, Groups A, B, C and D, SIPLUS system S7-300**, Model(s) 6AG1312-5BE03-2AY0, 6AG1313-5BF03-2AY0, 6AG1313-6CF03-2AY0, 6AG1314-1AG14-2AY0, 6AG1314-6CG03-2AY0, 6AG1315-2AH14-2AY0, 6AG1315-2EH14-2AY0, 6AG1315-2EH14-7AB0, 6AG1315-2FJ14-2AB0, 6AG1315-2FJ14-2AY0, 6AG1315-6FF04-2AY0, 6AG1317-2EK14-2AY0, 6AG1317-2EK14-7AB0, 6AG1317-2FK14-2AB0, 6AG1317-2FK14-2AY0, 6AG1317-6FF03-2AY0, 6AG1321-7BH01-4AS0, 6AG1321-7RD00-4AB0, 6AG1322-8BF00-2AB0, 6AG1326-1BK02-2AY0, 6AG1326-2BF10-2AB0, 6AG1326-2BF10-2AY0, 6AG1331-1KF02-4AB0, 6AG1331-1KF02-7AB0, 6AG1331-7PF01-4AB0, 6AG1342-5DA03-7XE0, 6AG1343-1GX31-4XE0, 6AG1350-1AH03-2AY0

**Class I, Division 2, Groups A, B, C and D, SIPLUS system S7-300 PS**, Model(s) 6AG1307-1EA01-7AA0

**Class I, Division 2, Groups A, B, C and D, SIPLUS System S7-300 PS**, Model(s) 6AG1307-1KA02-7AA0

**Class I, Division 2, Groups A, B, C and D, SIPLUS system S7-400**, Model(s) 6AG1405-0KA02-2AA0, 6AG1405-0KA02-7AA0, 6AG1405-0KR02-7AA0, 6AG1407-0KA02-4AA0, 6AG1407-0KA02-7AA0, 6AG1407-0KR02-4AA0, 6AG1407-0KR02-7AA0, 6AG1443-1EX30-4XE0, 6AG1443-1GX30-4XE0, 6AG1443-5DX05-4XE0, 6AG1443-5FX02-4XE0

**I/O modules**, Model(s) 6AG1195-7HD10-4XA0, I/O modules, 6AG1331-7KF02-2AB0, I/O modules, 6AG1331-7NF00-2AB0, I/O modules, 6AG1331-7NF10-2AB0, I/O modules, 6AG1331-7PF01-2AB0, I/O modules, 6AG1332-5HF00-2AB0, I/O modules

Last Updated on 2019-12-16

Der Umstand, dass der Name oder das Produkt eines Unternehmens in dieser Datenbank aufgeführt ist, garantiert nicht, dass die Herstellung der jeweiligen Produkte dem Follow-Up-Service von UL unterliegt. Nur Produkte mit UL-Zeichen gelten als zertifiziert und sind vom Follow-Up-Service von UL abgedeckt. Prüfen Sie daher stets, ob ein Produkt das UL-Zeichen trägt.

UL gestattet die Weiterverwendung der im Online-Zertifizierungsverzeichnis enthaltenen Materialien unter den folgenden Bedingungen: 1. Alle Anleitungen, Baugruppen, Konstruktionen, Designs, Systeme und/oder Zertifizierungen (Dateien) müssen vollständig und auf nicht irreführende Weise ohne Manipulation der Daten (oder Zeichnungen) dargestellt werden. 2. Bei Weiterverwendung von Materialien muss der Vermerk „Aus dem Online-Zertifizierungsverzeichnis mit Genehmigung von UL nachgedruckt“ stets mit angegeben werden. Darüber hinaus muss das nachgedruckte Material einen Urheberrechtsvermerk in folgendem Format enthalten: "© 2019 UL LLC"