

Product	MLFB	FW-Version	Short Description
---------	------	------------	-------------------

PROFIBUS DP			
IM155-6 DP HF V4.2	6ES7 155-6BU01-0CN0	V4.2	Interface module IM 155-6 High Feature for ET 200SP electronic modules, configuration control, up to 32 I/O modules; station extension via ET-Connection; direct data exchange (also F); firmware V4.2

PROFINET IO			
IE/PB Link HA	6GK1 411-5BB00	V4.0	IE/PB LINK HA, gateway between Industrial Ethernet and PROFIBUS, PROFINET IO proxy with real-time communication, system redundancy S2, H-CiR, Time-of-day synchronization via SIMATIC method, NTP, SNMP V1, LLDP, S7 routing, data record routing, connection of up to 125 S7/DPV0/DPV1 slaves, support of DP/PA Link and DP/FF Link, 10/100 Mbps Fast Ethernet, MRP, 9.6 kbps to 12 Mbps PROFIBUS, firmware download via configuration tool, redundant power supply, conformal coating, expanded temperature range -40 to 70°C, firmware version V4.0
IE/PB Link PN IO	6GK1 411-5AB10	V4.0	IE/PB LINK PN IO, gateway between Industrial Ethernet and PROFIBUS, PROFINET IO proxy with real-time communication, Time-of-day synchronization via SIMATIC method, NTP, SNMP V1, LLDP, S7 routing, data record routing, connection of up to 64 S7/DPV0/DPV1 slaves, support of DP/PA Link and DP/FF Link, 10/100 Mbps Fast Ethernet, MRP, 9.6 kbps to 12 Mbps PROFIBUS, firmware download via configuration tool, redundant power supply, firmware version V4.0
IM155-6 PN HF V4.2	6ES7 155-6AU00-0CN0	V4.2	Interface module with PROFINET interface V2.3 (RT/IRT) with integrated 2-port switch with cycle time from 250 microseconds; 64 I/O modules including F-modules plus 16 ET 200AL modules via ET-Connection; media redundancy (MRP); configuration control via PLC; module replacement in operation (multi-hot swap); start with empty slots; isochronous mode; Shared Device on up to 4 PROFINET controllers; supports MSI/MSO; system redundancy S2; supports PROFinergy; user data up to max. 288 bytes per I/O module; supports module distribution; firmware V4.2

PROFINET IO			
IM155-6 PN/2 HF	6ES7 155-6AU01-0CN0	V4.2	Interface module with PROFINET interface V2.3 (RT/IRT) with integrated 2-port switch with cycle time from 250 microseconds; 64 I/O modules including F-modules plus 16 ET 200AL modules via ET-Connection; module to module communication (MtM); media redundancy (MRP); configuration control via PLC; module replacement in operation (multi-hot swap); start with empty slots; isochronous mode; Shared Device on up to 4 PROFINET controllers; supports MSI/MSO; system redundancy S2; supports PROFINergy; user data up to max. 288 bytes per I/O module; supports module distribution; firmware V4.2
IM155-6 PN/3 HF	6ES7 155-6AU30-0CN0	V4.2	Interface module with PROFINET interface V2.3 (RT/IRT) with integrated 3-port switch with cycle time from 250 microseconds; 64 I/O modules including F-modules plus 16 ET 200AL modules via ET-Connection; module to module communication (MtM); media redundancy (MRP); configuration control via PLC; module replacement in operation (multi-hot swap); start with empty slots; isochronous mode; Shared Device on up to 4 PROFINET controllers; supports MSI/MSO; system redundancy S2; supports PROFINergy; user data up to max. 288 bytes per I/O module; supports module distribution; local I/O coupling; firmware V4.2

IO Modules			
2RO NO/NC DC24..48V/5A AC24..230V/5A	6ES7 132-4HB13-0AB0		Digital output module 2x relay NO/NC DC24..48V/5A AC 24..230V/5A
DQ4 x 24VDC/2A HS V2.0 N/OVS	6ES7 132-6BD20-0CA0	V2.0	Digital output module DQ4 x 24VDC/2A HS; Operating modes: DQ HS - Oversampling - valve control; value status; configurable diagnostics; substitute value for output; supports PROFINET; isochronous mode; firmware V2.0
DQ4 x 24VDC/2A HS V2.0 PWM	6ES7 132-6BD20-0CA0	V2.0	Digital output module DQ4 x 24VDC/2A HS; Operating modes: Pulse width modulation; configurable diagnostics; substitute value for output; supports PROFINET; firmware V2.0
AI Energy Meter CT HF V8.0	6ES7 134-6PA01-0CU0	V8.0	Analog input module AI Energy Meter CT HF; 1, 2, or 3 phase measurement of current and voltage; current measurement by means of Rogowski coils or current-voltage transformer; voltage measurement /without voltage transformer; neutral conductor current; power; retentive energy meter continuous and periodic; operating hours count; channel-specific diagnostics; cyclic and acyclic measured values; limit monitoring; cyclic and acyclic measured values can be configured by user, cyclic measured values via EE@Industry; measurement of fundamental wave values; line analysis functions; measured value recording; power failure analysis (recording for power failure and return)
AI Energy Meter RC HF V8.0	6ES7 134-6PA21-0CU0	V8.0	Analog input module AI Energy Meter RC HF; 1, 2, or 3 phase measurement of current and voltage; current measurement by means of Rogowski coils or current-voltage transformer; voltage measurement /without voltage transformer; neutral conductor current; power; retentive energy meter continuous and periodic; operating hours count; channel-specific diagnostics; cyclic and acyclic measured values; limit monitoring; cyclic and acyclic measured values can be configured by user, cyclic measured values via EE@Industry; measurement of fundamental wave values; line analysis functions; measured value recording; power failure analysis (recording for power failure and return)
AI 4xRTD/TC 4xM12	6ES7 144-5KD50-0BA0	V1.0	Analog input module AI4 x U/I/RTD 4xM12; degree of protection IP65/67; 30 mm overall width; 16-bit; selectable diagnostics and hardware interrupt; supports PROFINET; value status (only in PROFINET); firmware V1.0
F-DS 0,1 - 0,4A HF 3DI/LC V1.2	3RK1 308-0CA00-0CP0	V1.2	Failsafe direct starter, electronic switching; electronic overload protection; up to 0.09kW / 400 V; 0.1A to 0.4A, Option: control module 3DI/LC; ProfiEnergy. Extended temperature range -25 ... 60°C, no corrosive ambient allowed; firmware V1.2

SCALANCE			
SCALANCE X200-4P IRT V5.5	6GK5 200-4AH00-2BA3	V5.5	SIEMENS 4-port switch (4 x POF); PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE X200-4P IRT V5.5	6GK5 200-4AH10-2BA3	V5.5	SIEMENS 4-port switch (4 x POF); PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE X201-3P IRT V5.5	6GK5 201-3BH00-2BA3	V5.5	SIEMENS 4-port switch (1 x RJ45 + 3 x POF); PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE X201-3P IRT V5.5	6GK5 201-3BH10-2BA3	V5.5	SIEMENS 4-port switch (1 x RJ45 + 3 x POF); PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE X201-3P IRT PRO V5.5	6GK5 201-3JR00-2BA6	V5.5	SIEMENS 4-port switch (1 x RJ45 + 3 x POF); PRO; PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE X201-3P IRT PRO V5.5	6GK5 201-3JR10-2BA6	V5.5	SIEMENS 4-port switch (1 x RJ45 + 3 x POF); PRO; PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE X202-2IRT V5.5	6GK5 202-2BB00-2BA3	V5.5	SIEMENS 4-port switch (2 x RJ45 + 2 x FO); PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE X202-2IRT V5.5	6GK5 202-2BB10-2BA3	V5.5	SIEMENS 4-port switch (2 x RJ45 + 2 x FO); PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE X202-2P IRT V5.5	6GK5 202-2BH00-2BA3	V5.5	SIEMENS 4-port switch (2 x RJ45 + 2 x POF); PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE X202-2P IRT V5.5	6GK5 202-2BH10-2BA3	V5.5	SIEMENS 4-port switch (2 x RJ45 + 2 x POF); PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE X202-2P IRT PRO V5.5	6GK5 202-2JR00-2BA6	V5.5	SIEMENS 4-port switch (2 x RJ45 + 2 x POF); PRO; PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE X202-2P IRT PRO V5.5	6GK5 202-2JR10-2BA6	V5.5	SIEMENS 4-port switch (2 x RJ45 + 2 x POF); PRO; PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml

SCALANCE			
SCALANCE X204IRT V5.5	6GK5 204-0BA00-2BA3	V5.5	SIEMENS 4-port switch (4 x RJ45); PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE X204IRT V5.5	6GK5 204-0BA10-2BA3	V5.5	SIEMENS 4-port switch (4 x RJ45); PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE X204IRT PRO V5.5	6GK5 204-0JA00-2BA6	V5.5	SIEMENS 4-port switch (4 x RJ45); PRO; PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE X204IRT PRO V5.5	6GK5 204-0JA10-2BA6	V5.5	SIEMENS 4-port switch (4 x RJ45); PRO; PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE XF204IRT V5.5	6GK5 204-0BA00-2BF2	V5.5	SIEMENS 4-port switch (4 x RJ45); PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; flat; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE XF204IRT V5.5	6GK5 204-0BA10-2BF2	V5.5	SIEMENS 4-port switch (4 x RJ45); PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; flat; firmware V5.5 GSDML-V2.34-Siemens-002A-SCALANCE_X200-20201202.xml
SCALANCE XF204-2BA IRT V5.5	6GK5 204-2AA00-2BD2	V5.5	SIEMENS 4-port switch (2 x bus adapter); PROFINET IO device; supports RT/IRT; PROFINET interface and 4 ports; firmware V5.5, configure all plugged adapters GSDML-V2.34-Siemens-002A-SCALANCE_X200_M-20201211.xml
SCALANCE XM408-4C V6.3	6GK5 408-4GP00-2AM2	V6.3	SIEMENS Managed switch with 8 Ports and 2 optional Port Extenders with 8 ports, supports RT; PROFINET interface with max. 24 Ports; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_XM400-20201014.xml
SCALANCE XM408-4C V6.4	6GK5 408-4GP00-2AM2	V6.4	SIEMENS Managed switch with 8 Ports and 2 optional Port Extenders with 8 ports, supports RT; PROFINET interface with max. 24 Ports; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_XM400-20201014.xml
SCALANCE XM408-4C V6.3	6GK5 408-4GQ00-2AM2	V6.3	SIEMENS Managed switch with 8 Ports and 2 optional Port Extenders with 8 ports, supports RT; PROFINET interface with max. 24 Ports; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_XM400-20201014.xml
SCALANCE XM408-4C V6.4	6GK5 408-4GQ00-2AM2	V6.4	SIEMENS Managed switch with 8 Ports and 2 optional Port Extenders with 8 ports, supports RT; PROFINET interface with max. 24 Ports; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_XM400-20201014.xml
SCALANCE XM408-8C V6.3	6GK5 408-8GR00-2AM2	V6.3	SIEMENS Managed switch with 8 Ports and 2 optional Port Extenders with 8 ports, supports RT; PROFINET interface with max. 24 Ports; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_XM400-20201014.xml

SCALANCE			
SCALANCE XM408-8C V6.4	6GK5 408-8GR00-2AM2	V6.4	SIEMENS Managed switch with 8 Ports and 2 optional Port Extenders with 8 ports, supports RT; PROFINET interface with max. 24 Ports; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_XM400-20201014.xml
SCALANCE XM408-8C V6.3	6GK5 408-8GS00-2AM2	V6.3	SIEMENS Managed switch with 8 Ports and 2 optional Port Extenders with 8 ports, supports RT; PROFINET interface with max. 24 Ports; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_XM400-20201014.xml
SCALANCE XM408-8C V6.4	6GK5 408-8GS00-2AM2	V6.4	SIEMENS Managed switch with 8 Ports and 2 optional Port Extenders with 8 ports, supports RT; PROFINET interface with max. 24 Ports; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_XM400-20201014.xml
SCALANCE XM416-4C V6.3	6GK5 416-4GR00-2AM2	V6.3	SIEMENS Managed switch with 16 Ports and 1 optional Port Extender with 8 ports, supports RT; PROFINET interface with max. 24 Ports; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_XM400-20201014.xml
SCALANCE XM416-4C V6.4	6GK5 416-4GR00-2AM2	V6.4	SIEMENS Managed switch with 16 Ports and 1 optional Port Extender with 8 ports, supports RT; PROFINET interface with max. 24 Ports; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_XM400-20201014.xml
SCALANCE XM416-4C V6.3	6GK5 416-4GS00-2AM2	V6.3	SIEMENS Managed switch with 16 Ports and 1 optional Port Extender with 8 ports, supports RT; PROFINET interface with max. 24 Ports; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_XM400-20201014.xml
SCALANCE XM416-4C V6.4	6GK5 416-4GS00-2AM2	V6.4	SIEMENS Managed switch with 16 Ports and 1 optional Port Extender with 8 ports, supports RT; PROFINET interface with max. 24 Ports; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_XM400-20201014.xml
SCALANCE XR524-8C V6.3	6GK5 524-8GR00-2AR2	V6.3	SIEMENS Managed switch with 16 Gbit ports and 8 combo ports, with Layer 3 functionality; supports RT; PROFINET interface with max. 24 Ports; 24V DC; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR524-8C V6.4	6GK5 524-8GR00-2AR2	V6.4	SIEMENS Managed switch with 16 Gbit ports and 8 combo ports, with Layer 3 functionality; supports RT; PROFINET interface with max. 24 Ports; 24V DC; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR524-8C V6.3	6GK5 524-8GR00-3AR2	V6.3	SIEMENS Managed switch with 16 Gbit ports and 8 combo ports, with Layer 3 functionality; supports RT; PROFINET interface with max. 24 Ports; 240V; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR524-8C V6.4	6GK5 524-8GR00-3AR2	V6.4	SIEMENS Managed switch with 16 Gbit ports and 8 combo ports, with Layer 3 functionality; supports RT; PROFINET interface with max. 24 Ports; 240V; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml

SCALANCE			
SCALANCE XR524-8C V6.3	6GK5 524-8GR00-4AR2	V6.3	SIEMENS Managed switch with 16 Gbit ports and 8 combo ports, with Layer 3 functionality; supports RT; PROFINET interface with max. 24 Ports; 240V redundant; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR524-8C V6.4	6GK5 524-8GR00-4AR2	V6.4	SIEMENS Managed switch with 16 Gbit ports and 8 combo ports, with Layer 3 functionality; supports RT; PROFINET interface with max. 24 Ports; 240V redundant; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR524-8C V6.3	6GK5 524-8GS00-2AR2	V6.3	SIEMENS Managed switch with 16 Gbit ports and 8 combo ports, supports KEY-PLUG for Layer 3 functionality; supports RT; PROFINET interface with max. 24 Ports; 24V DC; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR524-8C V6.4	6GK5 524-8GS00-2AR2	V6.4	SIEMENS Managed switch with 16 Gbit ports and 8 combo ports, supports KEY-PLUG for Layer 3 functionality; supports RT; PROFINET interface with max. 24 Ports; 24V DC; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR524-8C V6.3	6GK5 524-8GS00-3AR2	V6.3	SIEMENS Managed switch with 16 Gbit ports and 8 combo ports, supports KEY-PLUG for Layer 3 functionality; supports RT; PROFINET interface with max. 24 Ports; 240V; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR524-8C V6.4	6GK5 524-8GS00-3AR2	V6.4	SIEMENS Managed switch with 16 Gbit ports and 8 combo ports, supports KEY-PLUG for Layer 3 functionality; supports RT; PROFINET interface with max. 24 Ports; 240V; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR524-8C V6.3	6GK5 524-8GS00-4AR2	V6.3	SIEMENS Managed switch with 16 Gbit ports and 8 combo ports, supports KEY-PLUG for Layer 3 functionality; supports RT; PROFINET interface with max. 24 Ports; 240V redundant; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR524-8C V6.4	6GK5 524-8GS00-4AR2	V6.4	SIEMENS Managed switch with 16 Gbit ports and 8 combo ports, supports KEY-PLUG for Layer 3 functionality; supports RT; PROFINET interface with max. 24 Ports; 240V redundant; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR526-8C V6.3	6GK5 526-8GR00-2AR2	V6.3	SIEMENS Managed switch with 16 Gbit ports, 8 combo ports and 2 SFP+ ports, with Layer 3 functionality; supports RT; PROFINET interface with max. 26 Ports; 24V DC; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml

SCALANCE			
SCALANCE XR526-8C V6.4	6GK5 526-8GR00-2AR2	V6.4	SIEMENS Managed switch with 16 Gbit ports,8 combo ports and 2 SFP+ ports, with Layer 3 functionality; supports RT; PROFINET interface with max. 26 Ports; 24V DC; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR526-8C V6.3	6GK5 526-8GR00-3AR2	V6.3	SIEMENS Managed switch with 16 Gbit ports,8 combo ports and 2 SFP+ ports, with Layer 3 functionality; supports RT; PROFINET interface with max. 26 Ports; 240V; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR526-8C V6.4	6GK5 526-8GR00-3AR2	V6.4	SIEMENS Managed switch with 16 Gbit ports,8 combo ports and 2 SFP+ ports, with Layer 3 functionality; supports RT; PROFINET interface with max. 26 Ports; 240V; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR526-8C V6.3	6GK5 526-8GR00-4AR2	V6.3	SIEMENS Managed switch with 16 Gbit ports,8 combo ports and 2 SFP+ ports, with Layer 3 functionality; supports RT; PROFINET interface with max. 26 Ports; 240V redundant; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR526-8C V6.4	6GK5 526-8GR00-4AR2	V6.4	SIEMENS Managed switch with 16 Gbit ports,8 combo ports and 2 SFP+ ports, with Layer 3 functionality; supports RT; PROFINET interface with max. 26 Ports; 240V redundant; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR526-8C V6.3	6GK5 526-8GS00-2AR2	V6.3	SIEMENS Managed switch with 16 Gbit ports,8 combo ports and 2 SFP+ ports, supports KEY-PLUG for Layer 3 functionality; supports RT; PROFINET interface with max. 26 Ports; 24V DC; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR526-8C V6.4	6GK5 526-8GS00-2AR2	V6.4	SIEMENS Managed switch with 16 Gbit ports,8 combo ports and 2 SFP+ ports, supports KEY-PLUG for Layer 3 functionality; supports RT; PROFINET interface with max. 26 Ports; 24V DC; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR526-8C V6.3	6GK5 526-8GS00-3AR2	V6.3	SIEMENS Managed switch with 16 Gbit ports,8 combo ports and 2 SFP+ ports, supports KEY-PLUG for Layer 3 functionality; supports RT; PROFINET interface with max. 26 Ports; 240V; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR526-8C V6.4	6GK5 526-8GS00-3AR2	V6.4	SIEMENS Managed switch with 16 Gbit ports,8 combo ports and 2 SFP+ ports, supports KEY-PLUG for Layer 3 functionality; supports RT; PROFINET interface with max. 26 Ports; 240V; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml

SCALANCE			
SCALANCE XR526-8C V6.3	6GK5 526-8GS00-4AR2	V6.3	SIEMENS Managed switch with 16 Gbit ports,8 combo ports and 2 SFP+ ports, supports KEY-PLUG for Layer 3 functionality; supports RT; PROFINET interface with max. 26 Ports; 240V redundant; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR526-8C V6.4	6GK5 526-8GS00-4AR2	V6.4	SIEMENS Managed switch with 16 Gbit ports,8 combo ports and 2 SFP+ ports, supports KEY-PLUG for Layer 3 functionality; supports RT; PROFINET interface with max. 26 Ports; 240V redundant; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR528-6M V6.3	6GK5 528-0AA00-2AR2	V6.3	SIEMENS Managed switch with 4 SFP+ ports and 6 module slots each with 4 Ports, supports RT; PROFINET interface with max. 28 Ports; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR528-6M V6.4	6GK5 528-0AA00-2AR2	V6.4	SIEMENS Managed switch with 4 SFP+ ports and 6 module slots each with 4 Ports, supports RT; PROFINET interface with max. 28 Ports; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR528-6M V6.3	6GK5 528-0AA00-2HR2	V6.3	SIEMENS Cable outlet rear; Managed switch with 4 SFP+ ports and 6 module slots each with 4 Ports, supports RT; PROFINET interface with max. 28 Ports; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR528-6M V6.4	6GK5 528-0AA00-2HR2	V6.4	SIEMENS Cable outlet rear; Managed switch with 4 SFP+ ports and 6 module slots each with 4 Ports, supports RT; PROFINET interface with max. 28 Ports; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR528-6M V6.3	6GK5 528-0AR00-2AR2	V6.3	SIEMENS Managed switch with 4 SFP+ ports and 6 module slots each with 4 Ports, with Layer 3 functionality, supports RT; PROFINET interface with max. 28 Ports; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR528-6M V6.4	6GK5 528-0AR00-2AR2	V6.4	SIEMENS Managed switch with 4 SFP+ ports and 6 module slots each with 4 Ports, with Layer 3 functionality, supports RT; PROFINET interface with max. 28 Ports; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR528-6M V6.3	6GK5 528-0AR00-2HR2	V6.3	SIEMENS Cable outlet rear; Managed switch with 4 SFP+ ports and 6 module slots each with 4 Ports, with Layer 3 functionality, supports RT; PROFINET interface with max. 28 Ports; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR528-6M V6.4	6GK5 528-0AR00-2HR2	V6.4	SIEMENS Cable outlet rear; Managed switch with 4 SFP+ ports and 6 module slots each with 4 Ports, with Layer 3 functionality, supports RT; PROFINET interface with max. 28 Ports; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml

SCALANCE			
SCALANCE XR552-12M V6.3	6GK5 552-0AA00-2AR2	V6.3	SIEMENS Managed switch with 4 SFP+ ports and 12 module slots each with 4 Ports, supports RT; PROFINET interface with max. 52 Ports; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR552-12M V6.4	6GK5 552-0AA00-2AR2	V6.4	SIEMENS Managed switch with 4 SFP+ ports and 12 module slots each with 4 Ports, supports RT; PROFINET interface with max. 52 Ports; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR552-12M V6.3	6GK5 552-0AA00-2HR2	V6.3	SIEMENS Cable outlet rear; Managed switch with 4 SFP+ ports and 12 module slots each with 4 Ports, supports RT; PROFINET interface with max. 52 Ports; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR552-12M V6.4	6GK5 552-0AA00-2HR2	V6.4	SIEMENS Cable outlet rear; Managed switch with 4 SFP+ ports and 12 module slots each with 4 Ports, supports RT; PROFINET interface with max. 52 Ports; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR552-12M V6.3	6GK5 552-0AR00-2AR2	V6.3	SIEMENS Managed switch with 4 SFP+ ports and 12 module slots each with 4 Ports, with Layer3 functionality, supports RT; PROFINET interface with max. 52 Ports; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR552-12M V6.4	6GK5 552-0AR00-2AR2	V6.4	SIEMENS Managed switch with 4 SFP+ ports and 12 module slots each with 4 Ports, with Layer3 functionality, supports RT; PROFINET interface with max. 52 Ports; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR552-12M V6.3	6GK5 552-0AR00-2HR2	V6.3	SIEMENS Cable outlet rear; Managed switch with 4 SFP+ ports and 12 module slots each with 4 Ports, with Layer3 functionality, supports RT; PROFINET interface with max. 52 Ports; Firmware V6.3 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XR552-12M V6.4	6GK5 552-0AR00-2HR2	V6.4	SIEMENS Cable outlet rear; Managed switch with 4 SFP+ ports and 12 module slots each with 4 Ports, with Layer3 functionality, supports RT; PROFINET interface with max. 52 Ports; Firmware V6.4 GSDML-V2.4-Siemens-002A-SCALANCE_X500-20210325.xml
SCALANCE XB205-3 V4.2	6GK5 205-3BB00-2AB2	V4.2	SIEMENS 8-port switch (5 x RJ45 + 3 x FO ST); PROFINET IO device; PROFINET interface and 8 ports; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB205-3 V4.3	6GK5 205-3BB00-2AB2	V4.3	SIEMENS 8-port switch (5 x RJ45 + 3 x FO ST); PROFINET IO device; PROFINET interface and 8 ports; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml

SCALANCE			
SCALANCE XB205-3 V4.2	6GK5 205-3BB00-2TB2	V4.2	SIEMENS 8-port switch (5 x RJ45 + 3 x FO ST); EtherNet/IP device; PROFINET interface and 8 ports; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB205-3 V4.3	6GK5 205-3BB00-2TB2	V4.3	SIEMENS 8-port switch (5 x RJ45 + 3 x FO ST); EtherNet/IP device; PROFINET interface and 8 ports; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB205-3 V4.2	6GK5 205-3BD00-2AB2	V4.2	SIEMENS 8-port switch (5 x RJ45 + 3 x FO SC); PROFINET IO device; PROFINET interface and 8 ports; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB205-3 V4.3	6GK5 205-3BD00-2AB2	V4.3	SIEMENS 8-port switch (5 x RJ45 + 3 x FO SC); PROFINET IO device; PROFINET interface and 8 ports; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB205-3 V4.2	6GK5 205-3BD00-2TB2	V4.2	SIEMENS 8-port switch (5 x RJ45 + 3 x FO SC); EtherNet/IP device; PROFINET interface and 8 ports; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB205-3 V4.3	6GK5 205-3BD00-2TB2	V4.3	SIEMENS 8-port switch (5 x RJ45 + 3 x FO SC); EtherNet/IP device; PROFINET interface and 8 ports; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB205-3 LD V4.2	6GK5 205-3BF00-2AB2	V4.2	SIEMENS 8-port switch (5 x RJ45 + 3 x FO LD); PROFINET IO device; PROFINET interface and 8 ports; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB205-3 LD V4.3	6GK5 205-3BF00-2AB2	V4.3	SIEMENS 8-port switch (5 x RJ45 + 3 x FO LD); PROFINET IO device; PROFINET interface and 8 ports; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB205-3 LD V4.2	6GK5 205-3BF00-2TB2	V4.2	SIEMENS 8-port switch (5 x RJ45 + 3 x FO LD); EtherNet/IP device; PROFINET interface and 8 ports; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB205-3 LD V4.3	6GK5 205-3BF00-2TB2	V4.3	SIEMENS 8-port switch (5 x RJ45 + 3 x FO LD); EtherNet/IP device; PROFINET interface and 8 ports; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB208 V4.2	6GK5 208-0BA00-2AB2	V4.2	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB208 V4.3	6GK5 208-0BA00-2AB2	V4.3	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml

SCALANCE			
SCALANCE XB208 V4.2	6GK5 208-0BA00-2TB2	V4.2	SIEMENS 8-port switch (8 x RJ45); EtherNet/IP device; PROFINET interface and 8 ports; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB208 V4.3	6GK5 208-0BA00-2TB2	V4.3	SIEMENS 8-port switch (8 x RJ45); EtherNet/IP device; PROFINET interface and 8 ports; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB213-3 V4.2	6GK5 213-3BB00-2AB2	V4.2	SIEMENS 16-port switch (13 x RJ45 + 3 x FO ST); PROFINET IO device; PROFINET interface and 16 ports; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB213-3 V4.3	6GK5 213-3BB00-2AB2	V4.3	SIEMENS 16-port switch (13 x RJ45 + 3 x FO ST); PROFINET IO device; PROFINET interface and 16 ports; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB213-3 V4.2	6GK5 213-3BB00-2TB2	V4.2	SIEMENS 16-port switch (13 x RJ45 + 3 x FO ST); EtherNet/IP device; PROFINET interface and 16 ports; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB213-3 V4.3	6GK5 213-3BB00-2TB2	V4.3	SIEMENS 16-port switch (13 x RJ45 + 3 x FO ST); EtherNet/IP device; PROFINET interface and 16 ports; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB213-3 V4.2	6GK5 213-3BD00-2AB2	V4.2	SIEMENS 16-port switch (13 x RJ45 + 3 x FO SC); PROFINET IO device; PROFINET interface and 16 ports; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB213-3 V4.3	6GK5 213-3BD00-2AB2	V4.3	SIEMENS 16-port switch (13 x RJ45 + 3 x FO SC); PROFINET IO device; PROFINET interface and 16 ports; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB213-3 V4.2	6GK5 213-3BD00-2TB2	V4.2	SIEMENS 16-port switch (13 x RJ45 + 3 x FO SC); EtherNet/IP device; PROFINET interface and 16 ports; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB213-3 V4.3	6GK5 213-3BD00-2TB2	V4.3	SIEMENS 16-port switch (13 x RJ45 + 3 x FO SC); EtherNet/IP device; PROFINET interface and 16 ports; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB213-3 LD V4.2	6GK5 213-3BF00-2AB2	V4.2	SIEMENS 16-port switch (13 x RJ45 + 3 x FO LD); PROFINET IO device; PROFINET interface and 16 ports; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB213-3 LD V4.3	6GK5 213-3BF00-2AB2	V4.3	SIEMENS 16-port switch (13 x RJ45 + 3 x FO LD); PROFINET IO device; PROFINET interface and 16 ports; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml

SCALANCE			
SCALANCE XB213-3 LD V4.2	6GK5 213-3BF00-2TB2	V4.2	SIEMENS 16-port switch (13 x RJ45 + 3 x FO LD); EtherNet/IP device; PROFINET interface and 16 ports; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB213-3 LD V4.3	6GK5 213-3BF00-2TB2	V4.3	SIEMENS 16-port switch (13 x RJ45 + 3 x FO LD); EtherNet/IP device; PROFINET interface and 16 ports; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB216 V4.2	6GK5 216-0BA00-2AB2	V4.2	SIEMENS 16-port switch (16 x RJ45); PROFINET IO device; PROFINET interface and 16 ports; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB216 V4.3	6GK5 216-0BA00-2AB2	V4.3	SIEMENS 16-port switch (16 x RJ45); PROFINET IO device; PROFINET interface and 16 ports; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB216 V4.2	6GK5 216-0BA00-2TB2	V4.2	SIEMENS 16-port switch (16 x RJ45); EtherNet/IP device; PROFINET interface and 16 ports; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XB216 V4.3	6GK5 216-0BA00-2TB2	V4.3	SIEMENS 16-port switch (16 x RJ45); EtherNet/IP device; PROFINET interface and 16 ports; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XB200-20201026.xml
SCALANCE XC206-2 V4.2	6GK5 206-2BB00-2AC2	V4.2	SIEMENS 8-port switch (6 x RJ45 + 2 x FO ST); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 V4.3	6GK5 206-2BB00-2AC2	V4.3	SIEMENS 8-port switch (6 x RJ45 + 2 x FO ST); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 V4.2	6GK5 206-2BD00-2AC2	V4.2	SIEMENS 8-port switch (6 x RJ45 + 2 x FO SC); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 V4.3	6GK5 206-2BD00-2AC2	V4.3	SIEMENS 8-port switch (6 x RJ45 + 2 x FO SC); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 SFP V4.2	6GK5 206-2BS00-2AC2	V4.2	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml

SCALANCE			
SCALANCE XC206-2 SFP V4.3	6GK5 206-2BS00-2AC2	V4.3	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 SFP EEC V4.2	6GK5 206-2BS00-2FC2	V4.2	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 SFP EEC V4.3	6GK5 206-2BS00-2FC2	V4.3	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 SFP G V4.2	6GK5 206-2GS00-2AC2	V4.2	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 SFP G V4.3	6GK5 206-2GS00-2AC2	V4.3	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 SFP G V4.2	6GK5 206-2GS00-2TC2	V4.2	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 SFP G V4.3	6GK5 206-2GS00-2TC2	V4.3	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 SFP G V4.2	6GK5 206-2GS00-2FC2	V4.2	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 SFP G V4.3	6GK5 206-2GS00-2FC2	V4.3	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml

SCALANCE			
SCALANCE XC206-2 SFP G PoE V4.2	6GK5 206-2RS00-2AC2	V4.2	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 SFP G PoE V4.3	6GK5 206-2RS00-2AC2	V4.3	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 SFP G PoE V4.2	6GK5 206-2RS00-5AC2	V4.2	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; 54V DC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 SFP G PoE V4.3	6GK5 206-2RS00-5AC2	V4.3	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; 54V DC; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 SFPG EEC POE 54V V4.2	6GK5 206-2RS00-5FC2	V4.2	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; 54V DC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC206-2 SFPG EEC POE 54V V4.3	6GK5 206-2RS00-5FC2	V4.3	SIEMENS 8-port switch (6 x RJ45 + 2 x SFP); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; 54V DC; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC208 V4.2	6GK5 208-0BA00-2AC2	V4.2	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC208 V4.3	6GK5 208-0BA00-2AC2	V4.3	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC208 EEC V4.2	6GK5 208-0BA00-2FC2	V4.2	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml

SCALANCE			
SCALANCE XC208 EEC V4.3	6GK5 208-0BA00-2FC2	V4.3	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC208 G V4.2	6GK5 208-0GA00-2AC2	V4.2	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC208 G V4.3	6GK5 208-0GA00-2AC2	V4.3	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC208 G V4.2	6GK5 208-0GA00-2TC2	V4.2	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC208 G V4.3	6GK5 208-0GA00-2TC2	V4.3	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC208 G EEC V4.2	6GK5 208-0GA00-2FC2	V4.2	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC208 G EEC V4.3	6GK5 208-0GA00-2FC2	V4.3	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC208 G PoE V4.2	6GK5 208-0RA00-2AC2	V4.2	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC208 G PoE V4.3	6GK5 208-0RA00-2AC2	V4.3	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml

SCALANCE			
SCALANCE XC208 G PoE V4.2	6GK5 208-0RA00-5AC2	V4.2	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; 54V DC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC208 G PoE V4.3	6GK5 208-0RA00-5AC2	V4.3	SIEMENS 8-port switch (8 x RJ45); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; 54V DC; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC216 V4.2	6GK5 216-0BA00-2AC2	V4.2	SIEMENS 16-port switch (16 x RJ45); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC216 V4.3	6GK5 216-0BA00-2AC2	V4.3	SIEMENS 16-port switch (16 x RJ45); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC216 EEC V4.2	6GK5 216-0BA00-2FC2	V4.2	SIEMENS 16-port switch (16 x RJ45); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC216 EEC V4.3	6GK5 216-0BA00-2FC2	V4.3	SIEMENS 16-port switch (16 x RJ45); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC216-3 SFP G PoE V4.3	6GK5 216-3RS00-2AC2	V4.3	SIEMENS 19-port switch (16 x RJ45 + 3 x SFP); PROFINET IO device; PROFINET interface and 19 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC216-3 SFP G PoE V4.3	6GK5 216-3RS00-5AC2	V4.3	SIEMENS 19-port switch (16 x RJ45 + 3 x SFP); PROFINET IO device; PROFINET interface and 19 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; 54V DC; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC216-4C V4.2	6GK5 216-4BS00-2AC2	V4.2	SIEMENS 16 Port Switch (12 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml

SCALANCE			
SCALANCE XC216-4C V4.3	6GK5 216-4BS00-2AC2	V4.3	SIEMENS 16 Port Switch (12 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC216-4C G V4.2	6GK5 216-4GS00-2AC2	V4.2	SIEMENS 16 Port Switch (12 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC216-4C G V4.3	6GK5 216-4GS00-2AC2	V4.3	SIEMENS 16 Port Switch (12 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC216-4C G EEC V4.2	6GK5 216-4GS00-2FC2	V4.2	SIEMENS 16 Port Switch (12 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC216-4C G EEC V4.3	6GK5 216-4GS00-2FC2	V4.3	SIEMENS 16 Port Switch (12 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC216-4C G EIP V4.2	6GK5 216-4GS00-2TC2	V4.2	SIEMENS 16 Port Switch (12 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC216-4C G EIP V4.3	6GK5 216-4GS00-2TC2	V4.3	SIEMENS 16 Port Switch (12 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC224 V4.2	6GK5 224-0BA00-2AC2	V4.2	SIEMENS 24-port switch (24 x RJ45); PROFINET IO device; PROFINET interface and 24 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC224 V4.3	6GK5 224-0BA00-2AC2	V4.3	SIEMENS 24-port switch (24 x RJ45); PROFINET IO device; PROFINET interface and 24 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml

SCALANCE			
SCALANCE XC224-4C G V4.2	6GK5 224-4GS00-2AC2	V4.2	SIEMENS 24 Port Switch (20 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 24 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC224-4C G V4.3	6GK5 224-4GS00-2AC2	V4.3	SIEMENS 24 Port Switch (20 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 24 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC224-4C G EEC V4.2	6GK5 224-4GS00-2FC2	V4.2	SIEMENS 24 Port Switch (20 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 24 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC224-4C G EEC V4.3	6GK5 224-4GS00-2FC2	V4.3	SIEMENS 24 Port Switch (20 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 24 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC224-4C G EIP V4.2	6GK5 224-4GS00-2TC2	V4.2	SIEMENS 24 Port Switch (20 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 24 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XC224-4C G EIP V4.3	6GK5 224-4GS00-2TC2	V4.3	SIEMENS 24 Port Switch (20 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 24 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XC200-20210310.xml
SCALANCE XF204-2BA V4.2	6GK5 204-2AA00-2GF2	V4.2	SIEMENS 4-port switch (2 x bus adapter); PROFINET IO device; PROFINET interface and 4 ports; S2-Device, supports CIR, HSync; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XF200-20210312.xml
SCALANCE XF204-2BA V4.3	6GK5 204-2AA00-2GF2	V4.3	SIEMENS 4-port switch (2 x bus adapter); PROFINET IO device; PROFINET interface and 4 ports; S2-Device, supports CIR, HSync; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XF200-20210312.xml
SCALANCE XF204-2BA V4.2	6GK5 204-2AA00-2YF2	V4.2	SIEMENS 4-port switch (2 x bus adapter); PROFINET IO device; PROFINET interface and 4 ports; S2-Device, supports CIR, HSync, DNA Redundanz; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XF200-20210312.xml
SCALANCE XF204-2BA V4.3	6GK5 204-2AA00-2YF2	V4.3	SIEMENS 4-port switch (2 x bus adapter); PROFINET IO device; PROFINET interface and 4 ports; S2-Device, supports CIR, HSync, DNA Redundanz; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XF200-20210312.xml

SCALANCE			
SCALANCE XP208 V4.2	6GK5 208-0HA00-2AS6	V4.2	SIEMENS 8-port switch (8 x M12); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XP208 V4.2	6GK5 208-0HA00-2AS6	V4.3	SIEMENS 8-port switch (8 x M12); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XP208 V4.2	6GK5 208-0HA00-2TS6	V4.2	SIEMENS 8-port switch (8 x M12); EtherNet/IP device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XP208 V4.3	6GK5 208-0HA00-2TS6	V4.3	SIEMENS 8-port switch (8 x M12); EtherNet/IP device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XP208EEC V4.2	6GK5 208-0HA00-2ES6	V4.2	SIEMENS 8-port switch (8 x M12); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XP208EEC V4.3	6GK5 208-0HA00-2ES6	V4.3	SIEMENS 8-port switch (8 x M12); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XP208PoE EEC V4.2	6GK5 208-0UA00-5ES6	V4.2	SIEMENS 8-port switch (8 x M12); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; supports PoE; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XP208PoE EEC V4.3	6GK5 208-0UA00-5ES6	V4.3	SIEMENS 8-port switch (8 x M12); PROFINET IO device; PROFINET interface and 8 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; supports PoE; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XP216 V4.2	6GK5 216-0HA00-2AS6	V4.2	SIEMENS 16-port switch (16 x M12); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml

SCALANCE			
SCALANCE XP216 V4.3	6GK5 216-0HA00-2AS6	V4.3	SIEMENS 16-port switch (16 x M12); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XP216 V4.2	6GK5 216-0HA00-2TS6	V4.2	SIEMENS 16-port switch (16 x M12); EtherNet/IP device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XP216 V4.3	6GK5 216-0HA00-2TS6	V4.3	SIEMENS 16-port switch (16 x M12); EtherNet/IP device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XP216EEC V4.2	6GK5 216-0HA00-2ES6	V4.2	SIEMENS 16-port switch (16 x M12); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XP216EEC V4.3	6GK5 216-0HA00-2ES6	V4.3	SIEMENS 16-port switch (16 x M12); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XP216PoE EEC V4.2	6GK5 216-0UA00-5ES6	V4.2	SIEMENS 16-port switch (16 x M12); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; supports PoE; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XP216PoE EEC V4.3	6GK5 216-0UA00-5ES6	V4.3	SIEMENS 16-port switch (16 x M12); PROFINET IO device; PROFINET interface and 16 ports; S2-Device, supports CIR; supports HSync; supports EtherNet/IP; supports PoE; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XP200-20210315.xml
SCALANCE XR324WG V4.2	6GK5 324-0BA00-2AR3	V4.2	SIEMENS 24-port switch (24 x RJ45); PROFINET IO device; PROFINET interface and 24 ports; supports EtherNet/IP; 24V DC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR324WG V4.3	6GK5 324-0BA00-2AR3	V4.3	SIEMENS 24-port switch (24 x RJ45); PROFINET IO device; PROFINET interface and 24 ports; supports EtherNet/IP; 24V DC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR324WG V4.2	6GK5 324-0BA00-3AR3	V4.2	SIEMENS 24-port switch (24 x RJ45); PROFINET IO device; PROFINET interface and 24 ports; supports EtherNet/IP; 230V AC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml

SCALANCE			
SCALANCE XR324WG V4.3	6GK5 324-0BA00-3AR3	V4.3	SIEMENS 24-port switch (24 x RJ45); PROFINET IO device; PROFINET interface and 24 ports; supports EtherNet/IP; 230V AC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR326-2C PoE WG V4.2	6GK5 326-2QS00-3AR3	V4.2	SIEMENS 26-port switch (24 x RJ45 + 2 x Combo); PROFINET IO device; PROFINET interface and 26 ports; supports EtherNet/IP; 24V DC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR326-2C PoE WG V4.3	6GK5 326-2QS00-3AR3	V4.3	SIEMENS 26-port switch (24 x RJ45 + 2 x Combo); PROFINET IO device; PROFINET interface and 26 ports; supports EtherNet/IP; 24V dC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR326-2C PoE WG V4.2	6GK5 326-2QS00-3RR3	V4.2	SIEMENS 26-port switch (24 x RJ45 + 2 x Combo); PROFINET IO device; PROFINET interface and 26 ports; supports EtherNet/IP; 230V AC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR326-2C PoE WG V4.3	6GK5 326-2QS00-3RR3	V4.3	SIEMENS 26-port switch (24 x RJ45 + 2 x Combo); PROFINET IO device; PROFINET interface and 26 ports; supports EtherNet/IP; 230V AC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR328-4C WG V4.2	6GK5 328-4FS00-2AR3	V4.2	SIEMENS 28-port switch (24 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 28 ports; supports EtherNet/IP; 24V DC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR328-4C WG V4.3	6GK5 328-4FS00-2AR3	V4.3	SIEMENS 28-port switch (24 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 28 ports; supports EtherNet/IP; 24V DC; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR328-4C WG V4.2	6GK5 328-4FS00-2RR3	V4.2	SIEMENS 28-port switch (24 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 28 ports; supports EtherNet/IP; 24V DC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR328-4C WG V4.3	6GK5 328-4FS00-2RR3	V4.3	SIEMENS 28-port switch (24 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 28 ports; supports EtherNet/IP; 24V DC; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR328-4C WG V4.2	6GK5 328-4FS00-3AR3	V4.2	SIEMENS 28-port switch (24 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 28 ports; supports EtherNet/IP; 230V AC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR328-4C WG V4.3	6GK5 328-4FS00-3AR3	V4.3	SIEMENS 28-port switch (24 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 28 ports; supports EtherNet/IP; 230V AC; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR328-4C WG V4.2	6GK5 328-4FS00-3RR3	V4.2	SIEMENS 28-port switch (24 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 28 ports; supports EtherNet/IP; 230V AC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml

SCALANCE			
SCALANCE XR328-4C WG V4.3	6GK5 328-4FS00-3RR3	V4.3	SIEMENS 28-port switch (24 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 28 ports; supports EtherNet/IP; 230V AC; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR328-4C WG V4.2	6GK5 328-4SS00-2AR3	V4.2	SIEMENS 28-port switch (24 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 28 ports; supports EtherNet/IP; 24V DC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR328-4C WG V4.3	6GK5 328-4SS00-2AR3	V4.3	SIEMENS 28-port switch (24 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 28 ports; supports EtherNet/IP; 24V DC; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR328-4C WG V4.2	6GK5 328-4SS00-3AR3	V4.2	SIEMENS 28-port switch (24 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 28 ports; supports EtherNet/IP; 230V AC; firmware V4.2 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml
SCALANCE XR328-4C WG V4.3	6GK5 328-4SS00-3AR3	V4.3	SIEMENS 28-port switch (24 x RJ45 + 4 x Combo); PROFINET IO device; PROFINET interface and 28 ports; supports EtherNet/IP; 230V AC; firmware V4.3 GSDML-V2.4-Siemens-002A-SCALANCE_XR300WG-20210311.xml