



[Residential External Mounted SPDs](#)



[Industrial and Commercial SPDs](#)

CROSS REFERENCE GUIDE

Surge Protective Devices

FirstSurge - FSPD

TPS3 - TPS4

usa.siemens.com/surge

This cross-reference file serves the purpose of mapping the relationships between different products, ensuring a seamless transition and maintaining continuity for end-users and stakeholders. As certain products are phased out, the cross-reference file helps identify equivalent or substitute products, guiding users towards suitable alternatives.

SIEMENS

FirstSurge - FSPD

More information:
[FSPD Datasheet](#)




Phased-Out SKU	Replacement SKU	Surge Current Rating	Type
—	US2:FSPD036	36 kA	Type 1 SPD
US2:FS060	US2:FSPD060	60 kA	Type 2 SPD
US2:FS100	US2:FSPD100	100 kA	Type 2 SPD
US2:FS140	US2:FSPD140	140 kA	Type 2 SPD

TPS3_01 Family - TPS4_01 Family

TPS3_02 Family - TPS4_01 Family

For Internal Mounting
Lighting Panels, Busway and MCC

More information:
[TPS4_01 Datasheet](#)



Phased-Out SKU	Replacement SKU	Features			Type
US2:TPS3A0110X002	US2:TPS4A0110X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3A0110X0B2	US2:TPS4A0110X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3A0110X0M2	US2:TPS4A0110X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3A0110XW02	US2:TPS4A0110XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3A0115X002	US2:TPS4A0115X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3A0115X0B2	US2:TPS4A0115X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3A0115X0M2	US2:TPS4A0115X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3A0115XW02	US2:TPS4A0115XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3A0120X002	US2:TPS4A0120X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3A0120X0B2	US2:TPS4A0120X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3A0120X0M2	US2:TPS4A0120X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3A0120XW02	US2:TPS4A0120XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3A0125X002	US2:TPS4A0125X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3A0125X0B2	US2:TPS4A0125X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3A0125X0M2	US2:TPS4A0125X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3A0125XW02	US2:TPS4A0125XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3A0130X002	US2:TPS4A0130X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3A0130X0B2	US2:TPS4A0130X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3A0130X0M2	US2:TPS4A0130X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3A0130XW02	US2:TPS4A0130XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3B0110X002	US2:TPS4B0110X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3B0110X0B2	US2:TPS4B0110X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3B0110X0M2	US2:TPS4B0110X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3B0110XW02	US2:TPS4B0110XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3B0115X002	US2:TPS4B0115X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3B0115X0B2	US2:TPS4B0115X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3B0115X0M2	US2:TPS4B0115X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3B0115XW02	US2:TPS4B0115XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3B0120X002	US2:TPS4B0120X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3B0120X0B2	US2:TPS4B0120X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3B0120X0M2	US2:TPS4B0120X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3B0120XW02	US2:TPS4B0120XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3B0125X002	US2:TPS4B0125X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3B0125X0B2	US2:TPS4B0125X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3B0125X0M2	US2:TPS4B0125X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3B0125XW02	US2:TPS4B0125XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD

TPS3_01 Family - TPS4_01 Family
TPS3_02 Family - TPS4_01 Family

[illegible]

TPS3_01 Family - TPS4_01 Family
TPS3_02 Family - TPS4_01 Family

[illegible]

TPS3_01 Family - TPS4_01 Family
TPS3_02 Family - TPS4_01 Family

[illegible]

TPS3_01 Family - TPS4_01 Family

TPS3_02 Family - TPS4_01 Family

Phased-Out SKU	Replacement SKU	Features			Type
US2:TPS3S0110XW02	US2:TPS4S0110XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3S0115X002	US2:TPS4S0115X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3S0115X0B2	US2:TPS4S0115X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3S0115X0M2	US2:TPS4S0115X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3S0115XW02	US2:TPS4S0115XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3S0120X002	US2:TPS4S0120X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3S0120X0B2	US2:TPS4S0120X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3S0120X0M2	US2:TPS4S0120X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3S0120XW02	US2:TPS4S0120XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3S0125X002	US2:TPS4S0125X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3S0125X0B2	US2:TPS4S0125X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3S0125X0M2	US2:TPS4S0125X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3S0125XW02	US2:TPS4S0125XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3S0130X002	US2:TPS4S0130X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3S0130X0B2	US2:TPS4S0130X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3S0130X0M2	US2:TPS4S0130X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3S0130XW02	US2:TPS4S0130XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3C0115XW00	US2:TPS4C0115XW00	Surge Counter	Terminal Lug	Standard Configuration	Type 1 SPD
US2:TPS3C0120XW00	US2:TPS4C0120XW00	Surge Counter	Terminal Lug	Standard Configuration	Type 1 SPD
US2:TPS3C0130XW00	US2:TPS4C0130XW00	Surge Counter	Terminal Lug	Standard Configuration	Type 1 SPD
US2:TPS3E0125XW00	US2:TPS4E0125XW00	Surge Counter	Terminal Lug	Standard Configuration	Type 1 SPD
US2:TPS3E0130XW00	US2:TPS4E0130XW00	Surge Counter	Terminal Lug	Standard Configuration	Type 1 SPD
US2:TPS3AL115X002	US2:TPS4AL115X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3AL115X0B2	US2:TPS4AL115X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3AL115X0M2	US2:TPS4AL115X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3AL115XW02	US2:TPS4AL115XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3AL130X002	US2:TPS4AL130X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3AL130X0B2	US2:TPS4AL130X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3AL130X0M2	US2:TPS4AL130X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3AL130XW02	US2:TPS4AL130XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3BL115X002	US2:TPS4BL115X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3BL115X0B2	US2:TPS4BL115X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3BL115X0M2	US2:TPS4BL115X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3BL115XW02	US2:TPS4BL115XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3BL130X002	US2:TPS4BL130X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3BL130X0B2	US2:TPS4BL130X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3BL130X0M2	US2:TPS4BL130X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3BL130XW02	US2:TPS4BL130XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3CL115X002	US2:TPS4CL115X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3CL115X0B2	US2:TPS4CL115X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3CL115X0M2	US2:TPS4CL115X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD
US2:TPS3CL115XW02	US2:TPS4CL115XW02	Surge Counter	Terminal Lug	Standard Configuration	Type 2 SPD
US2:TPS3CL130X002	US2:TPS4CL130X002	Surge Counter	Standard Configuration	Standard Configuration	Type 2 SPD
US2:TPS3CL130X0B2	US2:TPS4CL130X0B2	Surge Counter	Standard Configuration	Busway Application	Type 2 SPD
US2:TPS3CL130X0M2	US2:TPS4CL130X0M2	Surge Counter	Standard Configuration	MCC Application	Type 2 SPD

TPS3_02 Family - TPS4_01 Family

[illegible]

TPS3_02 Family - TPS4_01 Family

[illegible]

TPS3_03 Family - TPS4_03 Family

For External Mounting

Type 1 SPD

More information:

[TPS4_03 Datasheet](#)



Phased-Out SKU	Replacement SKU	Features		Type
US2:TPS3A030500	US2:TPS4A03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3A03050N	US2:TPS4A03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3A0305D0	US2:TPS4A03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3A0305DN	US2:TPS4A03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3B030500	US2:TPS4B03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3B03050N	US2:TPS4B03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3B0305D0	US2:TPS4B03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3B0305DN	US2:TPS4B03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3C030500	US2:TPS4C03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3C03050N	US2:TPS4C03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3C0305D0	US2:TPS4C03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3C0305DN	US2:TPS4C03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3D030500	US2:TPS4D03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3D0305D0	US2:TPS4D03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3E030500	US2:TPS4E03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3E03050N	US2:TPS4E03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3E0305D0	US2:TPS4E03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3E0305DN	US2:TPS4E03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3F030500	US2:TPS4F03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3F0305D0	US2:TPS4F03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3G030500	US2:TPS4G03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3G0305D0	US2:TPS4G03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3K030500	US2:TPS4K03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3K03050N	US2:TPS4K03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3K0305D0	US2:TPS4K03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3K0305DN	US2:TPS4K03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3L030500	US2:TPS4L03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3L03050N	US2:TPS4L03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3L0305D0	US2:TPS4L03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3L0305DN	US2:TPS4L03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3M0305	No Replacement			Type 1 SPD
US2:TPS3P0305	No Replacement			Type 1 SPD
US2:TPS3R0305	No Replacement			Type 1 SPD
US2:TPS3S030500	US2:TPS4S03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3S03050N	US2:TPS4S03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD


TPS3_03 Family - TPS4_03 Family

Phased-Out SKU	Replacement SKU	Features		Type
US2:TPS3S0305D0	US2:TPS4S03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3S0305DN	US2:TPS4S03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3H030500	No Replacement			Type 1 SPD
US2:TPS3J030500	No Replacement			Type 1 SPD
US2:TPS3F0305E0	US2:TPS4F03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3A03050	US2:TPS4A03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3F0305D	US2:TPS4F03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3F0305E0	US2:TPS4F03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD
US2:TPS3G03050	US2:TPS4G03050N	No Dry contact and audible alarm	N-G Protection	Type 1 SPD

TPS3_05 Family - TPS4_05 Family

For Internal Mounting
Power Panels and Switchboard Distribution

More information:
[TPS4_05 Datasheet](#)




Phased-Out SKU	Replacement SKU	Type
US2:TPS3A0510X2	US2:TPS4A0510X2	Type 2 SPD
US2:TPS3A0515X2	US2:TPS4A0515X2	Type 2 SPD
US2:TPS3A0520X2	US2:TPS4A0520X2	Type 2 SPD
US2:TPS3A0525X2	US2:TPS4A0525X2	Type 2 SPD
US2:TPS3A0530X2	US2:TPS4A0530X2	Type 2 SPD
US2:TPS3B0510X2	US2:TPS4B0510X2	Type 2 SPD
US2:TPS3B0515X2	US2:TPS4B0515X2	Type 2 SPD
US2:TPS3B0520X2	US2:TPS4B0520X2	Type 2 SPD
US2:TPS3B0525X2	US2:TPS4B0525X2	Type 2 SPD
US2:TPS3B0530X2	US2:TPS4B0530X2	Type 2 SPD
US2:TPS3C0510X2	US2:TPS4C0510X2	Type 2 SPD
US2:TPS3C0515X2	US2:TPS4C0515X2	Type 2 SPD
US2:TPS3C0520X2	US2:TPS4C0520X2	Type 2 SPD
US2:TPS3C0525X2	US2:TPS4C0525X2	Type 2 SPD
US2:TPS3C0530X2	US2:TPS4C0530X2	Type 2 SPD
US2:TPS3D0510X2	US2:TPS4D0510X2	Type 2 SPD
US2:TPS3D0515X2	US2:TPS4D0515X2	Type 2 SPD
US2:TPS3D0520X2	US2:TPS4D0520X2	Type 2 SPD
US2:TPS3D0525X2	US2:TPS4D0525X2	Type 2 SPD
US2:TPS3D0530X2	US2:TPS4D0530X2	Type 2 SPD
US2:TPS3E0510X2	US2:TPS4E0510X2	Type 2 SPD
US2:TPS3E0515X2	US2:TPS4E0515X2	Type 2 SPD
US2:TPS3E0520X2	US2:TPS4E0520X2	Type 2 SPD
US2:TPS3E0525X2	US2:TPS4E0525X2	Type 2 SPD
US2:TPS3E0530X2	US2:TPS4E0530X2	Type 2 SPD
US2:TPS3F0510X2	US2:TPS4F0510X2	Type 2 SPD
US2:TPS3F0515X2	US2:TPS4F0515X2	Type 2 SPD
US2:TPS3F0520X2	US2:TPS4F0520X2	Type 2 SPD
US2:TPS3F0525X2	US2:TPS4F0525X2	Type 2 SPD
US2:TPS3F0530X2	US2:TPS4F0530X2	Type 2 SPD
US2:TPS3G0510X2	US2:TPS4G0510X2	Type 2 SPD
US2:TPS3G0515X2	US2:TPS4G0515X2	Type 2 SPD
US2:TPS3K0510X2	US2:TPS4K0510X2	Type 2 SPD
US2:TPS3K0515X2	US2:TPS4K0515X2	Type 2 SPD
US2:TPS3K0520X2	US2:TPS4K0520X2	Type 2 SPD
US2:TPS3K0525X2	US2:TPS4K0525X2	Type 2 SPD

Phased-Out SKU	Replacement SKU	Type
US2:TPS3K0530X2	US2:TPS4K0530X2	Type 2 SPD
US2:TPS3L0510X2	US2:TPS4L0510X2	Type 2 SPD
US2:TPS3L0515X2	US2:TPS4L0515X2	Type 2 SPD
US2:TPS3L0520X2	US2:TPS4L0520X2	Type 2 SPD
US2:TPS3L0525X2	US2:TPS4L0525X2	Type 2 SPD
US2:TPS3L0530X2	US2:TPS4L0530X2	Type 2 SPD
US2:TPS3S0510X2	US2:TPS4S0510X2	Type 2 SPD
US2:TPS3S0515X2	US2:TPS4S0515X2	Type 2 SPD
US2:TPS3S0520X2	US2:TPS4S0520X2	Type 2 SPD
US2:TPS3S0525X2	US2:TPS4S0525X2	Type 2 SPD
US2:TPS3S0530X2	US2:TPS4S0530X2	Type 2 SPD
US2:TPS3A0515X0	US2:TPS4A0515X0	Type 1 SPD
US2:TPS3A0525X0	US2:TPS4A0525X0	Type 1 SPD
US2:TPS3B0515X0	US2:TPS4B0515X0	Type 1 SPD
US2:TPS3B0520X0	US2:TPS4B0520X0	Type 1 SPD
US2:TPS3C0515X0	US2:TPS4C0515X0	Type 1 SPD
US2:TPS3C0520X0	US2:TPS4C0520X0	Type 1 SPD
US2:TPS3C0530X0	US2:TPS4C0530X0	Type 1 SPD
US2:TPS3E0515X0	US2:TPS4E0515X0	Type 1 SPD
US2:TPS3E0520X0	US2:TPS4E0520X0	Type 1 SPD
US2:TPS3E0530X0	US2:TPS4E0530X0	Type 1 SPD
US2:TPS3F0515X0	US2:TPS4F0515X0	Type 1 SPD
US2:TPS3F0520X0	US2:TPS4F0520X0	Type 1 SPD
US2:TPS3F0525X0	US2:TPS4F0525X0	Type 1 SPD
US2:TPS3AL515X2	US2:TPS4AL515X2	Type 2 SPD
US2:TPS3AL530X2	US2:TPS4AL530X2	Type 2 SPD
US2:TPS3BL515X2	US2:TPS4BL515X2	Type 2 SPD
US2:TPS3BL530X2	US2:TPS4BL530X2	Type 2 SPD
US2:TPS3CL515X2	US2:TPS4CL515X2	Type 2 SPD
US2:TPS3CL530X2	US2:TPS4CL530X2	Type 2 SPD
US2:TPS3EL515X2	US2:TPS4EL515X2	Type 2 SPD
US2:TPS3EL530X2	US2:TPS4EL530X2	Type 2 SPD
US2:TPS3KL515X2	US2:TPS4KL515X2	Type 2 SPD
US2:TPS3KL530X2	US2:TPS4KL530X2	Type 2 SPD
US2:TPS3SL515X2	US2:TPS4SL515X2	Type 2 SPD
US2:TPS3SL530X2	US2:TPS4SL530X2	Type 2 SPD

TPS3_06 Family - TPS4_06 Family

For Internal Mounting
Switchboards and Low Voltage Switchgear

More information:
[TPS4_06 Datasheet](#)



Phased-Out SKU	Replacement SKU	Type
US2:TPS3A0610X02	US2:TPS4A0610X2	Type 2 SPD
US2:TPS3A0615X02	US2:TPS4A0615X2	Type 2 SPD
US2:TPS3A0620X02	US2:TPS4A0620X2	Type 2 SPD
US2:TPS3A0625X02	US2:TPS4A0625X2	Type 2 SPD
US2:TPS3A0630X02	US2:TPS4A0630X2	Type 2 SPD
US2:TPS3A0640X02	US2:TPS4A0640X2	Type 2 SPD
US2:TPS3A0640XB2	US2:TPS4A0640X2	Type 2 SPD
US2:TPS3A0640XM2	US2:TPS4A0640X2	Type 2 SPD
US2:TPS3A0650X02	US2:TPS4A0650X2	Type 2 SPD
US2:TPS3A0650XB2	US2:TPS4A0650X2	Type 2 SPD
US2:TPS3A0650XM2	US2:TPS4A0650X2	Type 2 SPD
US2:TPS3B0610X02	US2:TPS4B0610X2	Type 2 SPD
US2:TPS3B0615X02	US2:TPS4B0615X2	Type 2 SPD
US2:TPS3B0620X02	US2:TPS4B0620X2	Type 2 SPD
US2:TPS3B0625X02	US2:TPS4B0625X2	Type 2 SPD
US2:TPS3B0630X02	US2:TPS4B0630X2	Type 2 SPD
US2:TPS3B0640X02	US2:TPS4B0640X2	Type 2 SPD
US2:TPS3B0640XB2	US2:TPS4B0640X2	Type 2 SPD
US2:TPS3B0640XM2	US2:TPS4B0640X2	Type 2 SPD
US2:TPS3B0650X02	US2:TPS4B0650X2	Type 2 SPD
US2:TPS3B0650XB2	US2:TPS4B0650X2	Type 2 SPD
US2:TPS3B0650XM2	US2:TPS4B0650X2	Type 2 SPD
US2:TPS3C0610X02	US2:TPS4C0610X2	Type 2 SPD
US2:TPS3C0615X02	US2:TPS4C0615X2	Type 2 SPD
US2:TPS3C0620X02	US2:TPS4C0620X2	Type 2 SPD
US2:TPS3C0625X02	US2:TPS4C0625X2	Type 2 SPD
US2:TPS3C0630X02	US2:TPS4C0630X2	Type 2 SPD
US2:TPS3C0640X02	US2:TPS4C0640X2	Type 2 SPD
US2:TPS3C0640XB2	US2:TPS4C0640X2	Type 2 SPD
US2:TPS3C0640XM2	US2:TPS4C0640X2	Type 2 SPD
US2:TPS3C0650X02	US2:TPS4C0650X2	Type 2 SPD
US2:TPS3C0650XB2	US2:TPS4C0650X2	Type 2 SPD
US2:TPS3C0650XM2	US2:TPS4C0650X2	Type 2 SPD
US2:TPS3D0610X02	US2:TPS4D0610X2	Type 2 SPD
US2:TPS3D0615X02	US2:TPS4D0615X2	Type 2 SPD
US2:TPS3D0620X02	US2:TPS4D0620X2	Type 2 SPD

Phased-Out SKU	Replacement SKU	Type
US2:TPS3D0625X02	US2:TPS4D0625X2	Type 2 SPD
US2:TPS3D0630X02	US2:TPS4D0630X2	Type 2 SPD
US2:TPS3D0640X02	US2:TPS4D0640X2	Type 2 SPD
US2:TPS3D0640XB2	US2:TPS4D0640X2	Type 2 SPD
US2:TPS3D0640XM2	US2:TPS4D0640X2	Type 2 SPD
US2:TPS3E0610X02	US2:TPS4E0610X2	Type 2 SPD
US2:TPS3E0615X02	US2:TPS4E0615X2	Type 2 SPD
US2:TPS3E0620X02	US2:TPS4E0620X2	Type 2 SPD
US2:TPS3E0625X02	US2:TPS4E0625X2	Type 2 SPD
US2:TPS3E0630X02	US2:TPS4E0630X2	Type 2 SPD
US2:TPS3E0640X02	US2:TPS4E0640X2	Type 2 SPD
US2:TPS3E0640XB2	US2:TPS4E0640X2	Type 2 SPD
US2:TPS3E0640XM2	US2:TPS4E0640X2	Type 2 SPD
US2:TPS3E0650X02	US2:TPS4E0650X2	Type 2 SPD
US2:TPS3E0650XB2	US2:TPS4E0650X2	Type 2 SPD
US2:TPS3E0650XM2	US2:TPS4E0650X2	Type 2 SPD
US2:TPS3F0610X02	US2:TPS4F0610X2	Type 2 SPD
US2:TPS3F0615X02	US2:TPS4F0615X2	Type 2 SPD
US2:TPS3F0620X02	US2:TPS4F0620X2	Type 2 SPD
US2:TPS3F0625X02	US2:TPS4F0625X2	Type 2 SPD
US2:TPS3F0630X02	US2:TPS4F0630X2	Type 2 SPD
US2:TPS3F0640X02	US2:TPS4F0640X2	Type 2 SPD
US2:TPS3F0640XB2	US2:TPS4F0640X2	Type 2 SPD
US2:TPS3F0640XM2	US2:TPS4F0640X2	Type 2 SPD
US2:TPS3G0610X02	US2:TPS4G0610X2	Type 2 SPD
US2:TPS3G0615X02	US2:TPS4G0615X2	Type 2 SPD
US2:TPS3G0620X02	US2:TPS4G0620X2	Type 2 SPD
US2:TPS3G0620XB2	US2:TPS4G0620X2	Type 2 SPD
US2:TPS3G0620XM2	US2:TPS4G0620X2	Type 2 SPD
US2:TPS3G0625X02	US2:TPS4G0625X2	Type 2 SPD
US2:TPS3G0625XB2	US2:TPS4G0625X2	Type 2 SPD
US2:TPS3G0625XM2	US2:TPS4G0625X2	Type 2 SPD
US2:TPS3K0610X02	US2:TPS4K0610X2	Type 2 SPD
US2:TPS3K0615X02	US2:TPS4K0615X2	Type 2 SPD
US2:TPS3K0620X02	US2:TPS4K0620X2	Type 2 SPD
US2:TPS3K0625X02	US2:TPS4K0625X2	Type 2 SPD

TPS3_06 Family - TPS4_06 Family

Phased-Out SKU	Replacement SKU	Type
US2:TPS3K0630X02	US2:TPS4K0630X2	Type 2 SPD
US2:TPS3K0640X02	US2:TPS4K0640X2	Type 2 SPD
US2:TPS3K0640XB2	US2:TPS4K0640X2	Type 2 SPD
US2:TPS3K0640XM2	US2:TPS4K0640X2	Type 2 SPD
US2:TPS3K0650X02	US2:TPS4K0650X2	Type 2 SPD
US2:TPS3K0650XB2	US2:TPS4K0650X2	Type 2 SPD
US2:TPS3K0650XM2	US2:TPS4K0650X2	Type 2 SPD
US2:TPS3L0610X02	US2:TPS4L0610X2	Type 2 SPD
US2:TPS3L0615X02	US2:TPS4L0615X2	Type 2 SPD
US2:TPS3L0620X02	US2:TPS4L0620X2	Type 2 SPD
US2:TPS3L0625X02	US2:TPS4L0625X2	Type 2 SPD
US2:TPS3L0630X02	US2:TPS4L0630X2	Type 2 SPD
US2:TPS3L0640X02	US2:TPS4L0640X2	Type 2 SPD
US2:TPS3L0640XB2	US2:TPS4L0640X2	Type 2 SPD
US2:TPS3L0640XM2	US2:TPS4L0640X2	Type 2 SPD
US2:TPS3L0650X02	US2:TPS4L0650X2	Type 2 SPD
US2:TPS3L0650XB2	US2:TPS4L0650X2	Type 2 SPD
US2:TPS3L0650XM2	US2:TPS4L0650X2	Type 2 SPD
US2:TPS3S0610X02	US2:TPS4S0610X2	Type 2 SPD
US2:TPS3S0615X02	US2:TPS4S0615X2	Type 2 SPD
US2:TPS3S0620X02	US2:TPS4S0620X2	Type 2 SPD
US2:TPS3S0625X02	US2:TPS4S0625X2	Type 2 SPD
US2:TPS3S0630X02	US2:TPS4S0630X2	Type 2 SPD
US2:TPS3S0640X02	US2:TPS4S0640X2	Type 2 SPD
US2:TPS3S0640XB2	US2:TPS4S0640X2	Type 2 SPD
US2:TPS3S0640XM2	US2:TPS4S0640X2	Type 2 SPD
US2:TPS3S0650X02	US2:TPS4S0650X2	Type 2 SPD
US2:TPS3S0650XB2	US2:TPS4S0650X2	Type 2 SPD
US2:TPS3S0650XM2	US2:TPS4S0650X2	Type 2 SPD
US2:TPS3A0615X00	US2:TPS4A0615X0	Type 1 SPD
US2:TPS3C0615X00	US2:TPS4C0615X0	Type 1 SPD
US2:TPS3C0620X00	US2:TPS4C0620X0	Type 1 SPD
US2:TPS3C0625X00	US2:TPS4C0625X0	Type 1 SPD
US2:TPS3C0630X00	US2:TPS4C0630X0	Type 1 SPD
US2:TPS3C0650X00	US2:TPS4C0650X0	Type 1 SPD
US2:TPS3E0610X00	US2:TPS4C0610X0	Type 1 SPD
US2:TPS3E0620X00	US2:TPS4C0620X0	Type 1 SPD
US2:TPS3E0625X00	US2:TPS4C0625X0	Type 1 SPD
US2:TPS3E0630X00	US2:TPS4C0630X0	Type 1 SPD
US2:TPS3E0640X00	US2:TPS4C0640X0	Type 1 SPD
US2:TPS3E0650X00	US2:TPS4C0650X0	Type 1 SPD
US2:TPS3F0610X00	US2:TPS4F0610X0	Type 1 SPD
US2:TPS3F0615X00	US2:TPS4F0620X0	Type 1 SPD
US2:TPS3F0625X00	US2:TPS4F0625X0	Type 1 SPD
US2:TPS3F0630X00	US2:TPS4F0630X0	Type 1 SPD
US2:TPS3F0640X00	US2:TPS4F0640X0	Type 1 SPD
US2:TPS3L0625X00	US2:TPS4L0625X0	Type 1 SPD

Phased-Out SKU	Replacement SKU	Type
US2:TPS3L0640X00	US2:TPS4L0640X0	Type 1 SPD
US2:TPS3S0630X00	US2:TPS4L0630X0	Type 1 SPD
US2:TPS3AL615X02	US2:TPS4AL615X2	Type 2 SPD
US2:TPS3AL630X02	US2:TPS4AL630X2	Type 2 SPD
US2:TPS3AL645X02	US2:TPS4AL645X2	Type 2 SPD
US2:TPS3AL645XB2	US2:TPS4AL645X2	Type 2 SPD
US2:TPS3AL645XM2	US2:TPS4AL645X2	Type 2 SPD
US2:TPS3BL615X02	US2:TPS4BL615X2	Type 2 SPD
US2:TPS3BL630X02	US2:TPS4BL630X2	Type 2 SPD
US2:TPS3BL645X02	US2:TPS4BL645X2	Type 2 SPD
US2:TPS3BL645XB2	US2:TPS4BL645X2	Type 2 SPD
US2:TPS3BL645XM2	US2:TPS4BL645X2	Type 2 SPD
US2:TPS3CL615X02	US2:TPS4CL615X2	Type 2 SPD
US2:TPS3CL630X02	US2:TPS4CL630X2	Type 2 SPD
US2:TPS3CL645X02	US2:TPS4CL645X2	Type 2 SPD
US2:TPS3CL645XB2	US2:TPS4CL645X2	Type 2 SPD
US2:TPS3CL645XM2	US2:TPS4CL645X2	Type 2 SPD
US2:TPS3EL615X02	US2:TPS4CL615X2	Type 2 SPD
US2:TPS3EL630X02	US2:TPS4CL630X2	Type 2 SPD
US2:TPS3EL645X02	US2:TPS4CL645X2	Type 2 SPD
US2:TPS3EL645XB2	US2:TPS4CL645X2	Type 2 SPD
US2:TPS3EL645XM2	US2:TPS4CL645X2	Type 2 SPD
US2:TPS3KL615X02	US2:TPS4KL615X2	Type 2 SPD
US2:TPS3KL630X02	US2:TPS4KL630X2	Type 2 SPD
US2:TPS3KL645X02	US2:TPS4KL645X2	Type 2 SPD
US2:TPS3KL645XB2	US2:TPS4KL645X2	Type 2 SPD
US2:TPS3KL645XM2	US2:TPS4KL645X2	Type 2 SPD
US2:TPS3SL615X02	US2:TPS4SL615X2	Type 2 SPD
US2:TPS3SL630X02	US2:TPS4SL630X2	Type 2 SPD
US2:TPS3SL645X02	US2:TPS4SL645X2	Type 2 SPD
US2:TPS3SL645XB2	US2:TPS4SL645X2	Type 2 SPD
US2:TPS3SL645XM2	US2:TPS4SL645X2	Type 2 SPD
US2:TPS3E0630X2	US2:TPS4E0630X2	Type 2 SPD

TPS3_09 Family - TPS4_09 Family

For External Mounting

More information:

TPS4_09 Datasheet

[illegible]

TPS3_09 Family - TPS4_09 Family

[illegible]

TPS3_11 Family - TPS4_11 Family

For External Mounting

More information:

[TPS4_11 Datasheet](#)



Phased-Out SKU	Replacement SKU	Features	Type
US2:TPS3A111002	US2:TPS4A1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3A1110D2	US2:TPS4A1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3A111502	US2:TPS4A1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3A1115D2	US2:TPS4A1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3A112002	US2:TPS4A1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3A1120D2	US2:TPS4A1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3B111002	US2:TPS4B1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3B1110D2	US2:TPS4B1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3B111502	US2:TPS4B1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3B1115D2	US2:TPS4B1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3B112002	US2:TPS4B1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3B1120D2	US2:TPS4B1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3C111002	US2:TPS4C1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3C1110D2	US2:TPS4C1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3C111502	US2:TPS4C1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3C1115D2	US2:TPS4C1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3C112002	US2:TPS4C1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3C1120D2	US2:TPS4C1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3D111002	US2:TPS4D1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3D1110D2	US2:TPS4D1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3D111502	US2:TPS4D1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3D1115D2	US2:TPS4D1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3D112002	US2:TPS4D1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3D1120D2	US2:TPS4D1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3E111002	US2:TPS4E1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3E1110D2	US2:TPS4E1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3E111502	US2:TPS4E1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3E1115D2	US2:TPS4E1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3E112002	US2:TPS4E1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3E1120D2	US2:TPS4E1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3F111002	US2:TPS4F1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3F1110D2	US2:TPS4F1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3F111502	US2:TPS4F1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3F1115D2	US2:TPS4F1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3F112002	US2:TPS4F1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3F1120D2	US2:TPS4F1120D2	Dry contact and audible alarm	Type 2 SPD

TPS3_11 Family - TPS4_11 Family

Phased-Out SKU	Replacement SKU	Features	Type
US2:TPS3G111002	US2:TPS4G1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3G1110D2	US2:TPS4G1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3K111002	US2:TPS4K1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3K1110D2	US2:TPS4K1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3K111502	US2:TPS4K1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3K1115D2	US2:TPS4K1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3K112002	US2:TPS4K1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3K1120D2	US2:TPS4K1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3L111002	US2:TPS4L1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3L1110D2	US2:TPS4L1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3L111502	US2:TPS4L1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3L1115D2	US2:TPS4L1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3L112002	US2:TPS4L1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3L1120D2	US2:TPS4L1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3S111002	US2:TPS4S1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3S1110D2	US2:TPS4S1110D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3S111502	US2:TPS4S1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3S1115D2	US2:TPS4S1115D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3S112002	US2:TPS4S1120D2	Dry contact and audible alarm	Type 2 SPD
US2:TPS3S1120D2	US2:TPS4S1120D2	Dry contact and audible alarm	Type 2 SPD

TPS3_12 Family - TPS4_12 Family

For External Mounting

More information:

[TPS4_12 Datasheet](#)

If enclosure and disconnect are not required, select the TPS4_13 family.



Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3A12100X02	US2:TPS4A12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12100XD2	US2:TPS4A12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12100XT2	US2:TPS4A12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A1210FX02	US2:TPS4A12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1210FXD2	US2:TPS4A12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1210PX02	US2:TPS4A1210PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1210PXD2	US2:TPS4A1210PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1210SX02	US2:TPS4A1210SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1210SX02	US2:TPS4A1210SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1210VX02	US2:TPS4A1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1210VXD2	US2:TPS4A1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12150X02	US2:TPS4A12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12150XD2	US2:TPS4A12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12150XT2	US2:TPS4A12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A1215FX02	US2:TPS4A12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1215FXD2	US2:TPS4A12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1215PX02	US2:TPS4A1215PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1215PXD2	US2:TPS4A1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1215SX02	US2:TPS4A1215SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1215SX02	US2:TPS4A1215SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1215VX02	US2:TPS4A1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1215VXD2	US2:TPS4A1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12200X02	US2:TPS4A12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12200XD2	US2:TPS4A12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12200XT2	US2:TPS4A12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A1220FX02	US2:TPS4A12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1220FXD2	US2:TPS4A12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1220PX02	US2:TPS4A1220PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1220PXD2	US2:TPS4A1220PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1220SX02	US2:TPS4A1220SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1220SX02	US2:TPS4A1220SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1220VX02	US2:TPS4A1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1220VXD2	US2:TPS4A1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12250X02	US2:TPS4A12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12250XD2	US2:TPS4A12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12250XT2	US2:TPS4A12250XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3A1225FX02	US2:TPS4A12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1225FXD2	US2:TPS4A12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1225PX02	US2:TPS4A1225PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1225PXD2	US2:TPS4A1225PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1225SX02	US2:TPS4A1225SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1225SX02	US2:TPS4A1225SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1225VX02	US2:TPS4A1225VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1225VXD2	US2:TPS4A1225VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12300X02	US2:TPS4A12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12300XD2	US2:TPS4A12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12300XT2	US2:TPS4A12300XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A1230FX02	US2:TPS4A12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1230FXD2	US2:TPS4A12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1230PX02	US2:TPS4A1230PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1230PXD2	US2:TPS4A1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1230SX02	US2:TPS4A1230SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1230SX02	US2:TPS4A1230SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1230VX02	US2:TPS4A1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1230VXD2	US2:TPS4A1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12400X02	US2:TPS4A12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12400XD2	US2:TPS4A12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12400XT2	US2:TPS4A12400XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A1240FX02	US2:TPS4A12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1240FXD2	US2:TPS4A12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1240PX02	US2:TPS4A1240PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1240PXD2	US2:TPS4A1240PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1240SX02	US2:TPS4A1240SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1240SX02	US2:TPS4A1240SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1240VX02	US2:TPS4A1240VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1240VXD2	US2:TPS4A1240VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12500X02	US2:TPS4A12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12500XD2	US2:TPS4A12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A12500XT2	US2:TPS4A12500XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A1250FX02	US2:TPS4A12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1250FXD2	US2:TPS4A12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1250PX02	US2:TPS4A1250PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1250PXD2	US2:TPS4A1250PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1250SX02	US2:TPS4A1250SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1250SX02	US2:TPS4A1250SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1250VX02	US2:TPS4A1250VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3A1250VXD2	US2:TPS4A1250VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12100X02	US2:TPS4B12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12100XD2	US2:TPS4B12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12100XT2	US2:TPS4B12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B1210FX02	US2:TPS4B12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1210FXD2	US2:TPS4B12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1210PX02	US2:TPS4B1210PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3B1210PXD2	US2:TPS4B1210PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1210SX02	US2:TPS4B1210SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1210SXD2	US2:TPS4B1210SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1210VX02	US2:TPS4B1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1210VXD2	US2:TPS4B1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12150X02	US2:TPS4B12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12150XD2	US2:TPS4B12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12150XT2	US2:TPS4B12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B1215FX02	US2:TPS4B12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1215FXD2	US2:TPS4B12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1215PX02	US2:TPS4B1215PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1215PXD2	US2:TPS4B1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1215SX02	US2:TPS4B1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1215SXD2	US2:TPS4B1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1215VX02	US2:TPS4B1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1215VXD2	US2:TPS4B1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12200X02	US2:TPS4B12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12200XD2	US2:TPS4B12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12200XT2	US2:TPS4B12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B1220FX02	US2:TPS4B12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1220FXD2	US2:TPS4B12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1220PX02	US2:TPS4B1220PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1220PXD2	US2:TPS4B1220PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1220SX02	US2:TPS4B1220SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1220SXD2	US2:TPS4B1220SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1220VX02	US2:TPS4B1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1220VXD2	US2:TPS4B1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12250X02	US2:TPS4B12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12250XD2	US2:TPS4B12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12250XT2	US2:TPS4B12250XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B1225FX02	US2:TPS4B12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1225FXD2	US2:TPS4B12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1225PX02	US2:TPS4B1225PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1225PXD2	US2:TPS4B1225PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1225SX02	US2:TPS4B1225SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1225SXD2	US2:TPS4B1225SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1225VX02	US2:TPS4B1225VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1225VXD2	US2:TPS4B1225VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12300X02	US2:TPS4B12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12300XD2	US2:TPS4B12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12300XT2	US2:TPS4B12300XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B1230FX02	US2:TPS4B12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1230FXD2	US2:TPS4B12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1230PX02	US2:TPS4B1230PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1230PXD2	US2:TPS4B1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1230SX02	US2:TPS4B1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1230SXD2	US2:TPS4B1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3B1230VX02	US2:TPS4B1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1230VXD2	US2:TPS4B1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12400X02	US2:TPS4B12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12400XD2	US2:TPS4B12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12400XT2	US2:TPS4B12400XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B1240FX02	US2:TPS4B12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1240FXD2	US2:TPS4B12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1240PX02	US2:TPS4B1240PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1240PXD2	US2:TPS4B1240PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1240SX02	US2:TPS4B1240SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1240SXD2	US2:TPS4B1240SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1240VX02	US2:TPS4B1240VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1240VXD2	US2:TPS4B1240VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12500X02	US2:TPS4B12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12500XD2	US2:TPS4B12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B12500XT2	US2:TPS4B12500XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B1250FX02	US2:TPS4B12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1250FXD2	US2:TPS4B12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1250PX02	US2:TPS4B1250PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1250PXD2	US2:TPS4B1250PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1250SX02	US2:TPS4B1250SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1250SXD2	US2:TPS4B1250SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1250VX02	US2:TPS4B1250VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3B1250VXD2	US2:TPS4B1250VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12100X02	US2:TPS4C12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12100XD2	US2:TPS4C12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12100XT2	US2:TPS4C12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C1210FX02	US2:TPS4C12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1210FXD2	US2:TPS4C12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1210PX02	US2:TPS4C1210PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1210PXD2	US2:TPS4C1210PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1210SX02	US2:TPS4C1210SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1210SXD2	US2:TPS4C1210SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1210VX02	US2:TPS4C1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1210VXD2	US2:TPS4C1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12150X02	US2:TPS4C12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12150XD2	US2:TPS4C12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12150XT2	US2:TPS4C12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C1215FX02	US2:TPS4C12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1215FXD2	US2:TPS4C12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1215PX02	US2:TPS4C1215PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1215PXD2	US2:TPS4C1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1215SX02	US2:TPS4C1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1215SXD2	US2:TPS4C1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1215VX02	US2:TPS4C1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1215VXD2	US2:TPS4C1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12200X02	US2:TPS4C12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3C12200XD2	US2:TPS4C12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12200XT2	US2:TPS4C12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C1220FXD2	US2:TPS4C12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1220FXD2	US2:TPS4C12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1220PX02	US2:TPS4C1220PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1220PXD2	US2:TPS4C1220PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1220SX02	US2:TPS4C1220SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1220SXD2	US2:TPS4C1220SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1220VX02	US2:TPS4C1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1220VXD2	US2:TPS4C1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12250X02	US2:TPS4C12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12250XD2	US2:TPS4C12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12250XT2	US2:TPS4C12250XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C1225FX02	US2:TPS4C12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1225FXD2	US2:TPS4C12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1225PX02	US2:TPS4C1225PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1225PXD2	US2:TPS4C1225PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1225SX02	US2:TPS4C1225SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1225SXD2	US2:TPS4C1225SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1225VX02	US2:TPS4C1225VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1225VXD2	US2:TPS4C1225VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12300X02	US2:TPS4C12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12300XD2	US2:TPS4C12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12300XT2	US2:TPS4C12300XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C1230FX02	US2:TPS4C12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1230FXD2	US2:TPS4C12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1230PX02	US2:TPS4C1230PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1230PXD2	US2:TPS4C1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1230SX02	US2:TPS4C1230SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1230SXD2	US2:TPS4C1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1230VX02	US2:TPS4C1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1230VXD2	US2:TPS4C1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12400X02	US2:TPS4C12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12400XD2	US2:TPS4C12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12400XT2	US2:TPS4C12400XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C1240FX02	US2:TPS4C12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1240FXD2	US2:TPS4C12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1240PX02	US2:TPS4C1240PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1240PXD2	US2:TPS4C1240PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1240SX02	US2:TPS4C1240SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1240SXD2	US2:TPS4C1240SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1240VX02	US2:TPS4C1240VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1240VXD2	US2:TPS4C1240VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12500X02	US2:TPS4C12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12500XD2	US2:TPS4C12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12500XT2	US2:TPS4C12500XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C1250FX02	US2:TPS4C12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3C1250FXD2	US2:TPS4C12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1250PX02	US2:TPS4C1250PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1250PXD2	US2:TPS4C1250PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1250SX02	US2:TPS4C1250SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1250SXD2	US2:TPS4C1250SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1250VX02	US2:TPS4C1250VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C1250VXD2	US2:TPS4C1250VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D12100X02	US2:TPS4D12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D12100XD2	US2:TPS4D12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D12100XT2	US2:TPS4D12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3D1210FX02	US2:TPS4D12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3D1210FXD2	US2:TPS4D12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3D1210PX02	US2:TPS4D1210PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1210PXD2	US2:TPS4D1210PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1210SX02	US2:TPS4D1210SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1210SXD2	US2:TPS4D1210SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1210VX02	US2:TPS4D1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1210VXD2	US2:TPS4D1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D12150X02	US2:TPS4D12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D12150XD2	US2:TPS4D12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D12150XT2	US2:TPS4D12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3D1215FX02	US2:TPS4D12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3D1215FXD2	US2:TPS4D12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3D1215PX02	US2:TPS4D1215PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1215PXD2	US2:TPS4D1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1215SX02	US2:TPS4D1215SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1215SXD2	US2:TPS4D1215SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1215VX02	US2:TPS4D1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1215VXD2	US2:TPS4D1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D12200X02	US2:TPS4D12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D12200XD2	US2:TPS4D12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D12200XT2	US2:TPS4D12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3D1220FX02	US2:TPS4D12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3D1220FXD2	US2:TPS4D12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3D1220PX02	US2:TPS4D1220PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1220PXD2	US2:TPS4D1220PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1220SX02	US2:TPS4D1220SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1220SXD2	US2:TPS4D1220SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1220VX02	US2:TPS4D1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1220VXD2	US2:TPS4D1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D12250X02	US2:TPS4D12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D12250XD2	US2:TPS4D12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D12250XT2	US2:TPS4D12250XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3D1225FX02	US2:TPS4D12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3D1225FXD2	US2:TPS4D12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3D1225PX02	US2:TPS4D1225PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3D1225PXD2	US2:TPS4D1225PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD

TPS3_12 Family - TPS4_12 Family

[illegible]

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3E1215VXD2	US2:TPS4E1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E12200X02	US2:TPS4E12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E12200XD2	US2:TPS4E12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E12200XT2	US2:TPS4E12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E1220FX02	US2:TPS4E12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3E1220FXD2	US2:TPS4E12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3E1220PX02	US2:TPS4E1220PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1220PXD2	US2:TPS4E1220PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1220SX02	US2:TPS4E1220SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1220SX02	US2:TPS4E1220SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1220VX02	US2:TPS4E1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1220VXD2	US2:TPS4E1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E12250X02	US2:TPS4E12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E12250XD2	US2:TPS4E12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E12250XT2	US2:TPS4E12250XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E1225FX02	US2:TPS4E12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3E1225FXD2	US2:TPS4E12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3E1225PX02	US2:TPS4E1225PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1225PXD2	US2:TPS4E1225PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1225SX02	US2:TPS4E1225SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1225SX02	US2:TPS4E1225SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1225VX02	US2:TPS4E1225VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1225VXD2	US2:TPS4E1225VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E12300X02	US2:TPS4E12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E12300XD2	US2:TPS4E12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E12300XT2	US2:TPS4E12300XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E1230FX02	US2:TPS4E12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3E1230FXD2	US2:TPS4E12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3E1230PX02	US2:TPS4E1230PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1230PXD2	US2:TPS4E1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1230SX02	US2:TPS4E1230SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1230SX02	US2:TPS4E1230SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1230VX02	US2:TPS4E1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1230VXD2	US2:TPS4E1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E12400X02	US2:TPS4E12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E12400XD2	US2:TPS4E12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E12400XT2	US2:TPS4E12400XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E1240FX02	US2:TPS4E12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3E1240FXD2	US2:TPS4E12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3E1240PX02	US2:TPS4E1240PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1240PXD2	US2:TPS4E1240PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1240SX02	US2:TPS4E1240SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1240SX02	US2:TPS4E1240SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1240VX02	US2:TPS4E1240VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1240VXD2	US2:TPS4E1240VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E12500X02	US2:TPS4E12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E12500XD2	US2:TPS4E12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3E12500XT2	US2:TPS4E12500XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E1250FXD2	US2:TPS4E12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3E1250FXD2	US2:TPS4E12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3E1250PX02	US2:TPS4E1250PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1250PXD2	US2:TPS4E1250PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1250SX02	US2:TPS4E1250SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1250SXD2	US2:TPS4E1250SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1250VX02	US2:TPS4E1250VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3E1250VXD2	US2:TPS4E1250VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12100X02	US2:TPS4F12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12100XD2	US2:TPS4F12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12100XT2	US2:TPS4F12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F1210FX02	US2:TPS4F12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3F1210FXD2	US2:TPS4F12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3F1210PX02	US2:TPS4F1210PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1210PXD2	US2:TPS4F1210PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1210SX02	US2:TPS4F1210SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1210SXD2	US2:TPS4F1210SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1210VX02	US2:TPS4F1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1210VXD2	US2:TPS4F1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12150X02	US2:TPS4F12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12150XD2	US2:TPS4F12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12150XT2	US2:TPS4F12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F1215FX02	US2:TPS4F12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3F1215FXD2	US2:TPS4F12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3F1215PX02	US2:TPS4F1215PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1215PXD2	US2:TPS4F1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1215SX02	US2:TPS4F1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1215SXD2	US2:TPS4F1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1215VX02	US2:TPS4F1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1215VXD2	US2:TPS4F1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12200X02	US2:TPS4F12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12200XD2	US2:TPS4F12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12200XT2	US2:TPS4F12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F1220FX02	US2:TPS4F12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3F1220FXD2	US2:TPS4F12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3F1220PX02	US2:TPS4F1220PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1220PXD2	US2:TPS4F1220PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1220SX02	US2:TPS4F1220SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1220SXD2	US2:TPS4F1220SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1220VX02	US2:TPS4F1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1220VXD2	US2:TPS4F1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12250X02	US2:TPS4F12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12250XD2	US2:TPS4F12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12250XT2	US2:TPS4F12250XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F1225FX02	US2:TPS4F12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3F1225FXD2	US2:TPS4F12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3F1225PX02	US2:TPS4F1225PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1225PXD2	US2:TPS4F1225PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1225SX02	US2:TPS4F1225SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1225SXD2	US2:TPS4F1225SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1225VX02	US2:TPS4F1225VX02	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1225VXD2	US2:TPS4F1225VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12300X02	US2:TPS4F12300X02	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12300XD2	US2:TPS4F12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12300XT2	US2:TPS4F12300XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F1230FX02	US2:TPS4F12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3F1230FXD2	US2:TPS4F12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3F1230PX02	US2:TPS4F1230PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1230PXD2	US2:TPS4F1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1230SX02	US2:TPS4F1230SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1230SXD2	US2:TPS4F1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1230VX02	US2:TPS4F1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1230VXD2	US2:TPS4F1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12400X02	US2:TPS4F12400X02	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12400XD2	US2:TPS4F12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12400XT2	US2:TPS4F12400XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F1240FX02	US2:TPS4F12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3F1240FXD2	US2:TPS4F12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3F1240PX02	US2:TPS4F1240PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1240PXD2	US2:TPS4F1240PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1240SX02	US2:TPS4F1240SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1240SXD2	US2:TPS4F1240SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1240VX02	US2:TPS4F1240VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F1240VXD2	US2:TPS4F1240VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3G12100X02	US2:TPS4G12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3G12100XD2	US2:TPS4G12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3G12100XT2	US2:TPS4G12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3G1210FX02	US2:TPS4G12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3G1210FXD2	US2:TPS4G12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3G1210PX02	US2:TPS4G1210PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3G1210PXD2	US2:TPS4G1210PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3G1210SX02	US2:TPS4G1210SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3G1210SXD2	US2:TPS4G1210SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3G1210VX02	US2:TPS4G1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3G1210VXD2	US2:TPS4G1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3G12150X02	US2:TPS4G12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3G12150XD2	US2:TPS4G12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3G12150XT2	US2:TPS4G12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3G1215FX02	US2:TPS4G12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3G1215FXD2	US2:TPS4G12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3G1215PX02	US2:TPS4G1215PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3G1215PXD2	US2:TPS4G1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3G1215SX02	US2:TPS4G1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD

TPS3_12 Family - TPS4_12 Family

[illegible]

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3K12200X02	US2:TPS4K12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K12200XD2	US2:TPS4K12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K12200XT2	US2:TPS4K12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K1220FX02	US2:TPS4K12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3K1220FXD2	US2:TPS4K12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3K1220PX02	US2:TPS4K1220PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1220PXD2	US2:TPS4K1220PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1220SX02	US2:TPS4K1220SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1220SX02	US2:TPS4K1220SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1220VX02	US2:TPS4K1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1220VXD2	US2:TPS4K1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K12250X02	US2:TPS4K12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K12250XD2	US2:TPS4K12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K12250XT2	US2:TPS4K12250XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K1225FX02	US2:TPS4K12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3K1225FXD2	US2:TPS4K12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3K1225PX02	US2:TPS4K1225PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1225PXD2	US2:TPS4K1225PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1225SX02	US2:TPS4K1225SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1225SX02	US2:TPS4K1225SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1225VX02	US2:TPS4K1225VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1225VXD2	US2:TPS4K1225VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K12300X02	US2:TPS4K12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K12300XD2	US2:TPS4K12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K12300XT2	US2:TPS4K12300XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K1230FX02	US2:TPS4K12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3K1230FXD2	US2:TPS4K12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3K1230PX02	US2:TPS4K1230PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1230PXD2	US2:TPS4K1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1230SX02	US2:TPS4K1230SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1230SX02	US2:TPS4K1230SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1230VX02	US2:TPS4K1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1230VXD2	US2:TPS4K1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K12400X02	US2:TPS4K12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K12400XD2	US2:TPS4K12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K12400XT2	US2:TPS4K12400XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K1240FX02	US2:TPS4K12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3K1240FXD2	US2:TPS4K12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3K1240PX02	US2:TPS4K1240PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1240PXD2	US2:TPS4K1240PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1240SX02	US2:TPS4K1240SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1240SX02	US2:TPS4K1240SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1240VX02	US2:TPS4K1240VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1240VXD2	US2:TPS4K1240VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K12500X02	US2:TPS4K12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K12500XD2	US2:TPS4K12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K12500XT2	US2:TPS4K12500XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3K1250FX02	US2:TPS4K12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3K1250FXD2	US2:TPS4K12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3K1250PX02	US2:TPS4K1250PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1250PXD2	US2:TPS4K1250PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1250SX02	US2:TPS4K1250SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1250SXD2	US2:TPS4K1250SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1250VX02	US2:TPS4K1250VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3K1250VXD2	US2:TPS4K1250VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L12100X02	US2:TPS4L12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L12100XD2	US2:TPS4L12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L12100XT2	US2:TPS4L12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L1210FX02	US2:TPS4L12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3L1210FXD2	US2:TPS4L12100XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3L1210PX02	US2:TPS4L1210PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1210PXD2	US2:TPS4L1210PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1210SX02	US2:TPS4L1210SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1210SXD2	US2:TPS4L1210SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1210VX02	US2:TPS4L1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1210VXD2	US2:TPS4L1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L12150X02	US2:TPS4L12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L12150XD2	US2:TPS4L12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L12150XT2	US2:TPS4L12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L1215FX02	US2:TPS4L12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3L1215FXD2	US2:TPS4L12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3L1215PX02	US2:TPS4L1215PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1215PXD2	US2:TPS4L1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1215SX02	US2:TPS4L1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1215SXD2	US2:TPS4L1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1215VX02	US2:TPS4L1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1215VXD2	US2:TPS4L1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L12200X02	US2:TPS4L12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L12200XD2	US2:TPS4L12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L12200XT2	US2:TPS4L12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L1220FX02	US2:TPS4L12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3L1220FXD2	US2:TPS4L12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3L1220PX02	US2:TPS4L1220PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1220PXD2	US2:TPS4L1220PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1220SX02	US2:TPS4L1220SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1220SXD2	US2:TPS4L1220SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1220VX02	US2:TPS4L1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L1220VXD2	US2:TPS4L1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L12250X02	US2:TPS4L12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L12250XD2	US2:TPS4L12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3L12250XT2	US2:TPS4L12250XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L1225FX02	US2:TPS4L12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3L1225FXD2	US2:TPS4L12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3L1225PX02	US2:TPS4L1225PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD

TPS3_12 Family - TPS4_12 Family

[illegible]

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3S1210VX02	US2:TPS4S1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1210VXD2	US2:TPS4S1210VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12150X02	US2:TPS4S12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12150XD2	US2:TPS4S12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12150XT2	US2:TPS4S12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S1215FX02	US2:TPS4S12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S1215FXD2	US2:TPS4S12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S1215PX02	US2:TPS4S1215PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1215PXD2	US2:TPS4S1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1215SX02	US2:TPS4S1215SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1215SXD2	US2:TPS4S1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1215VX02	US2:TPS4S1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1215VXD2	US2:TPS4S1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12200X02	US2:TPS4S12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12200XD2	US2:TPS4S12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12200XT2	US2:TPS4S12200XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S1220FX02	US2:TPS4S12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S1220FXD2	US2:TPS4S12200XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S1220PX02	US2:TPS4S1220PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1220PXD2	US2:TPS4S1220PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1220SX02	US2:TPS4S1220SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1220SXD2	US2:TPS4S1220SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1220VX02	US2:TPS4S1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1220VXD2	US2:TPS4S1220VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12250X02	US2:TPS4S12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12250XD2	US2:TPS4S12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12250XT2	US2:TPS4S12250XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S1225FX02	US2:TPS4S12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S1225FXD2	US2:TPS4S12250XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S1225PX02	US2:TPS4S1225PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1225PXD2	US2:TPS4S1225PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1225SX02	US2:TPS4S1225SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1225SXD2	US2:TPS4S1225SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1225VX02	US2:TPS4S1225VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1225VXD2	US2:TPS4S1225VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12300X02	US2:TPS4S12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12300XD2	US2:TPS4S12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12300XT2	US2:TPS4S12300XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S1230FX02	US2:TPS4S12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S1230FXD2	US2:TPS4S12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S1230PX02	US2:TPS4S1230PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1230PXD2	US2:TPS4S1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1230SX02	US2:TPS4S1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1230SXD2	US2:TPS4S1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1230VX02	US2:TPS4S1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1230VXD2	US2:TPS4S1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12400X02	US2:TPS4S12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3S12400XD2	US2:TPS4S12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12400XT2	US2:TPS4S12400XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S1240FXD2	US2:TPS4S12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S1240FXD2	US2:TPS4S12400XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S1240PX02	US2:TPS4S1240PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1240PXD2	US2:TPS4S1240PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1240SX02	US2:TPS4S1240SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1240SXD2	US2:TPS4S1240SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1240VXD2	US2:TPS4S1240VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1240VXD2	US2:TPS4S1240VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12500XD2	US2:TPS4S12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12500XD2	US2:TPS4S12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S12500XT2	US2:TPS4S12500XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S1250FXD2	US2:TPS4S12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S1250FXD2	US2:TPS4S12500XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S1250PX02	US2:TPS4S1250PX02	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1250PXD2	US2:TPS4S1250PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1250SX02	US2:TPS4S1250SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1250SXD2	US2:TPS4S1250SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1250VXD2	US2:TPS4S1250VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3S1250VXD2	US2:TPS4S1250VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3F12300XD0	US2:TPS4F12300XD0	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 1 SPD
US2:TPS3A1215SXT2	US2:TPS4A1215SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A12100XD0	US2:TPS4A12100XD0	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 1 SPD
US2:TPS3C12300X00	US2:TPS4C12300XD0	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 1 SPD
US2:TPS3C1230PX00	US2:TPS4C1230PXD0	Pullbox	Surge Counter	Internal Disconnect		Type 1 SPD
US2:TPS3E1230PX00	US2:TPS4E1230PXD0	Pullbox	Surge Counter	Internal Disconnect		Type 1 SPD
US2:TPS3F12300XD0	US2:TPS4F12300XD0	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 1 SPD
US2:TPS3AL12150X02	US2:TPS4AL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3AL12150XD2	US2:TPS4AL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3AL12150XT2	US2:TPS4AL12150XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3AL1215FX02	US2:TPS4AL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3AL1215FXD2	US2:TPS4AL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3AL1215PX02	US2:TPS4AL1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3AL1215PXD2	US2:TPS4AL1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3AL1215SX02	US2:TPS4AL1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3AL1215SXD2	US2:TPS4AL1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3AL1215VXD2	US2:TPS4AL1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3AL1215VXD2	US2:TPS4AL1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3AL12300X02	US2:TPS4AL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3AL12300XD2	US2:TPS4AL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3AL12300XT2	US2:TPS4AL12300XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3AL1230FX02	US2:TPS4AL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3AL1230FXD2	US2:TPS4AL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3AL1230PX02	US2:TPS4AL1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3AL1230PXD2	US2:TPS4AL1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3AL1230SX02	US2:TPS4AL1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD

TPS3_12 Family - TPS4_12 Family

[illegible]

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3CL12150X02	US2:TPS4CL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL12150XD2	US2:TPS4CL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL12150XT2	US2:TPS4CL12150XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3CL1215FX02	US2:TPS4CL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3CL1215FXD2	US2:TPS4CL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3CL1215PX02	US2:TPS4CL1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1215PXD2	US2:TPS4CL1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1215SX02	US2:TPS4CL1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1215SXD2	US2:TPS4CL1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1215VX02	US2:TPS4CL1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1215VXD2	US2:TPS4CL1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL12300X02	US2:TPS4CL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL12300XD2	US2:TPS4CL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL12300XT2	US2:TPS4CL12300XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3CL1230FX02	US2:TPS4CL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3CL1230FXD2	US2:TPS4CL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3CL1230PX02	US2:TPS4CL1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1230PXD2	US2:TPS4CL1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1230SX02	US2:TPS4CL1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1230SXD2	US2:TPS4CL1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1230VX02	US2:TPS4CL1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1230VXD2	US2:TPS4CL1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL12450X02	US2:TPS4CL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL12450XD2	US2:TPS4CL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL12450XT2	US2:TPS4CL12450XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3CL1245FX02	US2:TPS4CL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3CL1245FXD2	US2:TPS4CL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3CL1245PX02	US2:TPS4CL1245PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1245PXD2	US2:TPS4CL1245PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1245SX02	US2:TPS4CL1245SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1245SXD2	US2:TPS4CL1245SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1245VX02	US2:TPS4CL1245VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3CL1245VXD2	US2:TPS4CL1245VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL12150X02	US2:TPS4EL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL12150XD2	US2:TPS4EL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL12150XT2	US2:TPS4EL12150XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3EL1215FX02	US2:TPS4EL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3EL1215FXD2	US2:TPS4EL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3EL1215PX02	US2:TPS4EL1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1215PXD2	US2:TPS4EL1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1215SX02	US2:TPS4EL1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1215SXD2	US2:TPS4EL1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1215VX02	US2:TPS4EL1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1215VXD2	US2:TPS4EL1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL12300X02	US2:TPS4EL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL12300XD2	US2:TPS4EL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL12300XT2	US2:TPS4EL12300XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3EL1230FX02	US2:TPS4EL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3EL1230FXD2	US2:TPS4EL1230XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3EL1230PX02	US2:TPS4EL1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1230PXD2	US2:TPS4EL1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1230SX02	US2:TPS4EL1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1230SXD2	US2:TPS4EL1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1230VX02	US2:TPS4EL1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1230VXD2	US2:TPS4EL1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL12450X02	US2:TPS4EL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL12450XD2	US2:TPS4EL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL12450XT2	US2:TPS4EL12450XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3EL1245FX02	US2:TPS4EL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3EL1245FXD2	US2:TPS4EL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3EL1245PX02	US2:TPS4EL1245PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1245PXD2	US2:TPS4EL1245PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1245SX02	US2:TPS4EL1245SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1245SXD2	US2:TPS4EL1245SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1245VX02	US2:TPS4EL1245VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3EL1245VXD2	US2:TPS4EL1245VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL12150X02	US2:TPS4KL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL12150XD2	US2:TPS4KL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL12150XT2	US2:TPS4KL12150XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3KL1215FX02	US2:TPS4KL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3KL1215FXD2	US2:TPS4KL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3KL1215PX02	US2:TPS4KL1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL1215PXD2	US2:TPS4KL1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL1215SX02	US2:TPS4KL1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL1215SXD2	US2:TPS4KL1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL1215VX02	US2:TPS4KL1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL1215VXD2	US2:TPS4KL1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL12300X02	US2:TPS4KL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL12300XD2	US2:TPS4KL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL12300XT2	US2:TPS4KL12300XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3KL1230FX02	US2:TPS4KL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3KL1230FXD2	US2:TPS4KL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3KL1230PX02	US2:TPS4KL1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL1230PXD2	US2:TPS4KL1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL1230SX02	US2:TPS4KL1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL1230SXD2	US2:TPS4KL1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL1230VX02	US2:TPS4KL1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL1230VXD2	US2:TPS4KL1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL12450X02	US2:TPS4KL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL12450XD2	US2:TPS4KL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL12450XT2	US2:TPS4KL12450XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3KL1245FX02	US2:TPS4KL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3KL1245FXD2	US2:TPS4KL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3KL1245PX02	US2:TPS4KL1245PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL1245PXD2	US2:TPS4KL1245PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL1245SX02	US2:TPS4KL1245SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD

TPS3_12 Family - TPS4_12 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3KL1245SXD2	US2:TPS4KL1245SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL1245VXD2	US2:TPS4KL1245VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3KL1245VXD2	US2:TPS4KL1245VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL12150XD2	US2:TPS4SL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL12150XD2	US2:TPS4SL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL12150XT2	US2:TPS4SL12150XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3SL1215FXD2	US2:TPS4SL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3SL1215FXD2	US2:TPS4SL12150XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3SL1215PXD2	US2:TPS4SL1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1215PXD2	US2:TPS4SL1215PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1215SX02	US2:TPS4SL1215SX02	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1215SXD2	US2:TPS4SL1215SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1215VXD2	US2:TPS4SL1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1215VXD2	US2:TPS4SL1215VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL12300XD2	US2:TPS4SL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL12300XD2	US2:TPS4SL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL12300XT2	US2:TPS4SL12300XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3SL1230FXD2	US2:TPS4SL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3SL1230FXD2	US2:TPS4SL12300XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3SL1230PXD2	US2:TPS4SL1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1230PXD2	US2:TPS4SL1230PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1230SX02	US2:TPS4SL1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1230SXD2	US2:TPS4SL1230SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1230VXD2	US2:TPS4SL1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1230VXD2	US2:TPS4SL1230VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL12450XD2	US2:TPS4SL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL12450XD2	US2:TPS4SL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL12450XT2	US2:TPS4SL12450XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3SL1245FXD2	US2:TPS4SL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3SL1245FXD2	US2:TPS4SL12450XD2	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3SL1245PXD2	US2:TPS4SL1245PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1245PXD2	US2:TPS4SL1245PXD2	Pullbox	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1245SX02	US2:TPS4SL1245SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1245SXD2	US2:TPS4SL1245SXD2	NEMA 4X Stainless Steel	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1245VXD2	US2:TPS4SL1245VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3SL1245VXD2	US2:TPS4SL1245VXD2	NEMA 4X non-metallic	Surge Counter	Internal Disconnect		Type 2 SPD
US2:TPS3C12200X00	US2:TPS4C12200XD0	Standard NEMA 4 Metallic	Surge Counter	Internal Disconnect		Type 1 SPD

TPS3_15 Family - TPS4_15 Family

For External Mounting

More information:

[TPS4_15 Datasheet](#)



Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3A151K0X02	US2:TPS4A151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A151K0XT2	US2:TPS4A151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A151KFX02	US2:TPS4A151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A151KPX02	US2:TPS4A151KPXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A151KSX02	US2:TPS4A151KSXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A151KVX02	US2:TPS4A151KVXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A15600X02	US2:TPS4A15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A15600XT2	US2:TPS4A15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A1560FX02	US2:TPS4A15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1560PX02	US2:TPS4A1560PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A1560SX02	US2:TPS4A1560SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A1560VX02	US2:TPS4A1560VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A15800X02	US2:TPS4A15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A15800XT2	US2:TPS4A15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A1580FX02	US2:TPS4A15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3A1580PX02	US2:TPS4A1580PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A1580SX02	US2:TPS4A1580SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3A1580VX02	US2:TPS4A1580VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B151K0X02	US2:TPS4B151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B151K0XT2	US2:TPS4B151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B151KFX02	US2:TPS4B151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B151KPX02	US2:TPS4B151KPXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B151KSX02	US2:TPS4B151KSXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B151KVX02	US2:TPS4B151KVXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B15600X02	US2:TPS4B15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B15600XT2	US2:TPS4B15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B1560FX02	US2:TPS4B15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1560PX02	US2:TPS4B1560PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B1560SX02	US2:TPS4B1560SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B1560VX02	US2:TPS4B1560VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B15800X02	US2:TPS4B15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B15800XT2	US2:TPS4B15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD

TPS3_15 Family - TPS4_15 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3B1580FX02	US2:TPS4B15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3B1580PX02	US2:TPS4B1580PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B1580SX02	US2:TPS4B1580SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3B1580VX02	US2:TPS4B1580VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C151K0X02	US2:TPS4C151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C151K0XT2	US2:TPS4C151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C151KFX02	US2:TPS4C151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C151KPX02	US2:TPS4C151KPXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C151KSX02	US2:TPS4C151KSXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C151KVX02	US2:TPS4C151KVXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C15600X02	US2:TPS4C15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C15600XT2	US2:TPS4C15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C1560FX02	US2:TPS4C15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1560PX02	US2:TPS4C1560PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C1560SX02	US2:TPS4C1560SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C1560VX02	US2:TPS4C1560VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C15800X02	US2:TPS4C15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C15800XT2	US2:TPS4C15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C1580FX02	US2:TPS4C15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3C1580PX02	US2:TPS4C1580PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C1580SX02	US2:TPS4C1580SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3C1580VX02	US2:TPS4C1580VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3D15600X02	US2:TPS4D15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3D15600XT2	US2:TPS4D15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3D1560FX02	US2:TPS4D15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3D1560PX02	US2:TPS4D1560PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3D1560SX02	US2:TPS4D1560SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3D1560VX02	US2:TPS4D1560VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3D15800X02	US2:TPS4D15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3D15800XT2	US2:TPS4D15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3D1580FX02	US2:TPS4D15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3D1580PX02	US2:TPS4D1580PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3D1580SX02	US2:TPS4D1580SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3D1580VX02	US2:TPS4D1580VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E151K0X02	US2:TPS4E151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E151K0XT2	US2:TPS4E151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E151KFX02	US2:TPS4E151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3E151KPX02	US2:TPS4E151KPXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E151KSX02	US2:TPS4E151KSXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E151KVX02	US2:TPS4E151KVXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E15600X02	US2:TPS4E15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E15600XT2	US2:TPS4E15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E1560FX02	US2:TPS4E15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3E1560PX02	US2:TPS4E1560PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E1560SX02	US2:TPS4E1560SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E1560VX02	US2:TPS4E1560VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E15800X02	US2:TPS4E15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD

TPS3_15 Family - TPS4_15 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3E15800XT2	US2:TPS4E15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E1580FX02	US2:TPS4E15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3E1580PX02	US2:TPS4E1580PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E1580SX02	US2:TPS4E1580SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3E1580VX02	US2:TPS4E1580VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F15600X02	US2:TPS4F15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F15600XT2	US2:TPS4F15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F1560FX02	US2:TPS4F15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3F1560PX02	US2:TPS4F1560PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F1560SX02	US2:TPS4F1560SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F1560VX02	US2:TPS4F1560VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F15800X02	US2:TPS4F15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F15800XT2	US2:TPS4F15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F1580FX02	US2:TPS4F15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3F1580PX02	US2:TPS4F1580PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F1580SX02	US2:TPS4F1580SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F1580VX02	US2:TPS4F1580VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3G15400X02	US2:TPS4G15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3G15400XT2	US2:TPS4G15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3G1540FX02	US2:TPS4G15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3G1540PX02	US2:TPS4G1560PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3G1540SX02	US2:TPS4G1560SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3G1540VX02	US2:TPS4G1560VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3G15500X02	US2:TPS4G15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3G15500XT2	US2:TPS4G15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3G1550FX02	US2:TPS4G15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3G1550PX02	US2:TPS4G1560PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3G1550SX02	US2:TPS4G1560SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3G1550VX02	US2:TPS4G1560VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K151K0X02	US2:TPS4K151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K151K0XT2	US2:TPS4K151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K151KFX02	US2:TPS4K151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3K151KPX02	US2:TPS4K151KPXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K151KSX02	US2:TPS4K151KSXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K151KVX02	US2:TPS4K151KVXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K15600X02	US2:TPS4K15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K15600XT2	US2:TPS4K15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K1560FX02	US2:TPS4K15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3K1560PX02	US2:TPS4K1560PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K1560SX02	US2:TPS4K1560SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K1560VX02	US2:TPS4K1560VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K15800X02	US2:TPS4K15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K15800XT2	US2:TPS4K15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K1580FX02	US2:TPS4K15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3K1580PX02	US2:TPS4K1580PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K1580SX02	US2:TPS4K1580SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3K1580VX02	US2:TPS4K1580VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD

TPS3_15 Family - TPS4_15 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3L151K0X02	US2:TPS4L151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L151K0XT2	US2:TPS4L151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L151KFX02	US2:TPS4L151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3L151KPX02	US2:TPS4L151KPXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L151KSX02	US2:TPS4L151KSXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L151KVX02	US2:TPS4L151KVXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L15600X02	US2:TPS4L15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L15600XT2	US2:TPS4L15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L1560FX02	US2:TPS4L15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3L1560PX02	US2:TPS4L1560PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L1560SX02	US2:TPS4L1560SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L1560VX02	US2:TPS4L1560VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L15800X02	US2:TPS4L15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L15800XT2	US2:TPS4L15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L1580FX02	US2:TPS4L15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3L1580PX02	US2:TPS4L1580PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L1580SX02	US2:TPS4L1580SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3L1580VX02	US2:TPS4L1580VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S151K0X02	US2:TPS4S151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S151K0XT2	US2:TPS4S151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S151KFX02	US2:TPS4S151K0XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S151KPX02	US2:TPS4S151KPXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S151KSX02	US2:TPS4S151KSXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S151KVX02	US2:TPS4S151KVXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S15600X02	US2:TPS4S15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S15600XT2	US2:TPS4S15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S1560FX02	US2:TPS4S15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S1560PX02	US2:TPS4S1560PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S1560SX02	US2:TPS4S1560SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S1560VX02	US2:TPS4S1560VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S15800X02	US2:TPS4S15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S15800XT2	US2:TPS4S15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S1580FX02	US2:TPS4S15800XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3S1580PX02	US2:TPS4S1580PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S1580SX02	US2:TPS4S1580SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3S1580VX02	US2:TPS4S1580VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3F15600X00	US2:TPS4F15600XT0	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 1 SPD
US2:TPS3AL15600X02	US2:TPS4AL15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3AL15600XT2	US2:TPS4AL15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3AL1560FX02	US2:TPS4AL15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3AL1560PX02	US2:TPS4AL1560PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3AL1560SX02	US2:TPS4AL1560SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3AL1560VX02	US2:TPS4AL1560VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3AL15900X02	US2:TPS4AL15900XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3AL15900XT2	US2:TPS4AL15900XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3AL1590FX02	US2:TPS4AL15900XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3AL1590PX02	US2:TPS4AL1590PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD

TPS3_15 Family - TPS4_15 Family

[illegible]

TPS3_15 Family - TPS4_15 Family

Phased-Out SKU	Replacement SKU	Features				Type
US2:TPS3KL1590PX02	US2:TPS4KL1590PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3KL1590SX02	US2:TPS4KL1590SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3KL1590VX02	US2:TPS4KL1590VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3SL15600X02	US2:TPS4SL15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3SL15600XT2	US2:TPS4SL15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3SL1560FX02	US2:TPS4SL15600XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3SL1560PX02	US2:TPS4SL1560PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3SL1560SX02	US2:TPS4SL1560SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3SL1560VX02	US2:TPS4SL1560VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3SL15900X02	US2:TPS4SL15900XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3SL15900XT2	US2:TPS4SL15900XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3SL1590FX02	US2:TPS4SL15900XT2	Standard NEMA 4 Metallic	Surge Counter	Thru-door disconnect	Add Flush kit accessory	Type 2 SPD
US2:TPS3SL1590PX02	US2:TPS4SL1590PXT2	Pullbox	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3SL1590SX02	US2:TPS4SL1590SXT2	NEMA 4X Stainless Steel	Surge Counter	Thru-door disconnect		Type 2 SPD
US2:TPS3SL1590VX02	US2:TPS4SL1590VXT2	NEMA 4X non-metallic	Surge Counter	Thru-door disconnect		Type 2 SPD

Notes

This image shows a single sheet of white paper with horizontal ruling lines. The lines are evenly spaced and run across the width of the page. There are no margins, text, or other markings on the paper.

[illegible]

Notes

This image shows a single sheet of white paper with horizontal ruling lines. The lines are evenly spaced and run across the width of the page. There are no margins, text, or other markings on the paper.

Legal Manufacturer

Siemens Industry, Inc.
3617 Parkway Ln
Peachtree Corners, GA 30092
United States of America

Telephone: +1 (800) 333-7421
www.usa.siemens.com/surge

Order No. RPRG-TPS34-0324

This document contains a general description of available technical options only, and its effectiveness will be subject to specific variables including field conditions and project parameters. Siemens does not make representations, warranties, or assurances as to the accuracy or completeness of the content contained herein. Siemens reserves the right to modify the technology and product specifications in its sole discretion without advance notice.