

Level Measurement

Continuous level measurement

Radar level transmitters / SITRANS LR150

Overview



SITRANS LR150 is a compact radar transmitter for continuous level measurement of liquids, slurries, and solids to a range of 15 m (49.2 ft).

Benefits

- Bluetooth connectivity for easy setup with SITRANS mobile IQ.
- Optional HMI with pushbutton programming and local diagnostic data.
- Chemically resistant PVDF sensor.
- HART 7.0 communication for intelligent integration into your application.
- W band FMCW radar yields narrow beam with small antenna for superior performance in short range applications.
- Approved for open air applications outside of a tank.
- 2 mm accuracy and zero near range distance yields optimum inventory management capability.
- Compact design fits in limited space installations.
- Hazardous area variants available for safe use in explosive gas or dust environments (pending).

Application

SITRANS LR150 is a W band FMCW radar level transmitter, with a chemically resistant PVDF sensor, for years of trouble-free, reliable measurement service.

4 to 20 mA loop powered with HART, providing accurate level measurement to ranges of 15 m (49.2 ft). Measurement is possible, non-intrusively, through plastic vessel tops for easy installation. Programming is convenient using the Bluetooth connection and SITRANS mobile IQ application on your smart device or locally with an optional HMI.

Level Measurement

Continuous level measurement

Radar level transmitters / SITRANS LR150

Selection and ordering data

SITRANS LR150 Radar level transmitter Non-contact, HART, 15 m (49.2 ft) range, for liquids and solids.		Article No. 7ML534 0 - ● A ● 0 7 - 4 ● ● ●											
Click on the Article No. for the online configuration in the PIA Life Cycle Portal.													
Bluetooth function													
Without						0							
With						1							
Process connection													
1-½" NPT									A				
R 1-½" (BSPT)									B				
G 1-½" (BSPP)									C				
Type of protection													
Non Ex (ordinary locations) ²⁾											A		
Ex i (ia) (Gas Ex-Zone 0/Class 1, Div. 1 & Div. 2) ¹⁾											C		
Electrical connections/cable entry													
M20												F	
½" NPT												K	
Local HMI													
Without display (closed lid of PBT/PC material)													0
With display (closed lid of PBT/PC material)													1
With display (clear lid with plastic window of PC material)													3

Selection and Ordering data	Order code
Further designs	
Please add "-Z" to Article No. and specify Order code(s).	
Tag (device parameter, max. 32 characters) plate stainless steel 304/1.4301	Y15
Inspection certificate 3.1 (EN 10204) - device with test data	C25
INMETRO, IA MASC	E25
NEPSI, COE	E27
EACEx	E24
ATEX, IECEX, cFM _{US} , cCSA _{US}	E49
CSA-Japan-Ex	E29
WHG and VLAREM II	E61

Accessories	Article No.
Operating Instructions	
All literature is available to download for free, in a range of languages, at http://www.siemens.com/processinstrumentation/documentation	
Accessories	
Bracket, 316L Stainless steel, 1 inch mount, 80 mm (3.1 inch) offset	A5E50507509
Bracket, 316L Stainless steel, 1 inch mount, 200 mm (7.9 inch) offset	A5E50507511
Bracket, 316L Stainless steel, 1.5 inch mount, 80 mm (3.1 inch) offset	A5E50507514
Bracket, 316L Stainless steel, 1.5 inch mount, 200 mm (7.9 inch) offset	A5E50507516
SITRANS LR150 HMI with connection cable	A5E50812988
SITRANS LR140/LR150 Blind lid with o-ring	A5E50822955
SITRANS LR150 clear lid with o-ring	A5E50822960
Flat gasket, FKM, for G1.5 inch sensor	A5E50822967
1-½ BSP locknut, plastic	7ML1830-1DP
SIMATIC RTU3030C compact, remote data manager with alarming	6NH3112-3BA00-0-XX0
Intrinsically Safe barrier	7NG4124-1AA00
SITRANS RD100, loop powered display - see Chapter 7	7ML5741-.....-

Level Measurement

Continuous level measurement

Radar level transmitters / SITRANS LR150

Selection and ordering data (continued)

Accessories	Article No.
SITRANS RD150, remote digital display for 4 to 20 mA and HART devices - see Chapter 7	7ML5742-.....
SITRANS RD200, universal input display with Modbus conversion - see Chapter 7	7ML5740-.....
SITRANS RD300, dual line display with totalizer and linearization curve and Modbus conversion- see Chapter 7	7ML5744-.....
For applicable back up point level switch -see point level measurement section	

¹⁾ Must be ordered in combination with order code E24, E25, E27, E49. or E29.

²⁾ Not available with order code E24, E25, E27, E49. or E29.


Technical specifications

SITRANS LR150	
Mode of operation	
Measuring principle	W band FMCW radar
Measuring range	0 ... 15 m (0 ... 49.2 ft)
Frequency	80 GHz nominal
Beam angle	8°
Power Supply	
HART	
• Voltage	12 ... 35 V DC
• Current	4 ... 20 mA
Communications	
4 ... 20 mA	HART 7.0
Accuracy	± 2 mm
Rated operating conditions	
Vessel pressure	-1 ... +3 bar (14.50 ... 43.51 psi g)
Ambient temperature	-40 ... +70 °C (-40 ... +158 °F)
Process temperature	-40 ... +80 °C (-40 ... +176 °F)
Storage temperature	-40 ... +80 °C (-40 ... +176 °F)
Design	
Weight	0.5 kg (1.1 lb)
Material (sensor)	PVDF
Material (enclosure)	PBT
Process connection	1-½" NPT, 1-½" BSPT or 1-½" BSPP
Degree of protection	IP66/IP67
Cable inlet	M20 or ½" NPT
Certificates and approvals	
Radio	CE, ATEX, IECEx, cFMUS, cCSAus, EAC, NEPSI, FDA/EG 1935/2004
Water monitoring, flow	CE, FCC, IC, Anatel, ICASA, NCC, KC, CITC, RCM, WPC, Telec, NBTC, MCMC
Canadian Registration Number (CRN)	MCERTS Class 1
British Columbia	0F22218.51
Alberta	0F20596.2
Saskatchewan	0F2002.3
Manitoba	0F7032.4
Ontario	0F22218.5
New Brunswick	0F05183.6
Nova Scotia	0F1490.07
Prince Edward Island	0F1490.08
Newfoundland and Labrador	0F1490.09
Yukon	0F1490.0
Northwest Territories	0F1490.0Y
Nunavut	0F1490.0T

Technical specifications (continued)


SITRANS LR150	
Programming	
SITRANS mobile IQ App	SITRANS mobile IQ is a Bluetooth app that provides an intuitive interface to quickly configure, set up and monitor SITRANS LR100 series (available for Android, Apple and Windows devices). For more information: http://www.siemens.com/mobileIQ
Optional HMI	4 button with display of variables and diagnostic data
SIMATIC PDM	SIMATIC PDM allows for remote PC configuration and diagnostics (for installation on a network).
SITRANS DTM	

Dimensional drawings




SITRANS LR150, dimensions in mm (inch)

Dimensional drawings (continued)



SITRANS LR150 mounting brackets, dimensions in mm (inch)

Circuit diagrams



SITRANS LR150 connections