

INDUSTRIAL ETHERNET

SCALANCE X –




Industrial Ethernet Switches

[siemens.com/switches](https://www.siemens.com/switches)

SIEMENS

Overview of the portfolio

PORTFOLIO

		Network components (SCALANCE X)				CSM (Compact Switch Module)	
Backbone Layer	X-500 managed	 XR-500WG / XR-500					
	X-400 managed	 XC-400					
Aggregation Layer	X-300 managed	 XC-300 / XCM-300 XR-300WG / XR-300PoE WG XR-300 / XRM-300					
	X-200 managed	 XB-200 XC-200 / G / PoE XP-200 / G / PoE / EEC XF204G XF-200BA XF-200					
Cell Layer	X-200IRT managed	 X-200RNA X-200IRT X-200IRT PRO XF-200IRT X-200P IRT				 LOGO! CSM CSM 1277 CSM 377	
	X-100 unmanaged	 XB-100 XC-100 / XC-100PoE XR-100WG / XR-100PoE WG XCM-100 Media converter					
	X-000 unmanaged	 X-000 XB-000					

G_IK10_XX_10255

Portfolio of the SCALANCE X Industrial Ethernet Switches and Compact Switch Modules (CSM)

	Layer 3 / Routing	19" design	Modular through media modules	Support of Gigabit Ethernet	Support of 10 Gbit/s	PROFINET	EtherNet/IP	Office features (VLAN)	Diagnostic functions	Isochronous Real-Time (IRT)	Power over Ethernet	Can be used under enhanced ambient conditions	Time synchronization to IEEE 1588	Additional interface for SIMATIC S7-300/ET 200M, S7-1200 or LOGO!
X-500	•	•	•	•	•	•	•	•	•				•	
X-400	•		•	•		•	•	•	•		•			
X-300		•	•	•	•	•	•	•	•		•	•	•	
X-200				•	•	•	•	•	•	•	•	•		
X-100		•		•	•						•			
X-000				•								•		
CSM														•

• applies to selected versions

G_IK10_XX_10302

With the Industrial Ethernet Switches you can meet specific challenges in a customized manner – our comprehensive product portfolio always has the right switch for you.

Today's requirements on an industrial communication network are manifold. Appropriate network components enable you to master every challenge:

- Secure and integrated communication across the entire company and across company limits
- Uninterrupted flow of information from the sensor/actuator level all the way to the enterprise level
- Fast data exchange between the plant components
- Availability of information at any location
- Easy and consistent configuration and efficient diagnostics, simple expansions and modernizations
- Integrated security functions which prevent unauthorized access
- 5 year warranty on all SCALANCE products
- Comprehensive consideration of cybersecurity measures in all phases of the product lifecycle

Find the right Industrial Ethernet Switches directly in the configurator – to the TIA Selection Tool: [siemens.com/tstcloud/](https://www.siemens.com/tstcloud/)

Further information concerning plugs: [siemens.com/plugs](https://www.siemens.com/plugs)

Further information concerning cabling: [siemens.com/fastconnect](https://www.siemens.com/fastconnect)

Further information concerning network management: [siemens.com/sinec](https://www.siemens.com/sinec)

Portfolio

UNMANAGED		
Compact Switch Modules CSM	SCALANCE X-000 unmanaged	SCALANCE X-100 unmanaged
More connection to SIMATIC	Space-saving, cost-efficient, and industrial-grade entry-level solution	For a reliable network solution with all equipment details
		
LOGO! CSM	SCALANCE X005/X005EEC	SCALANCE XB-100
		
CSM 1277	SCALANCE XB-000	SCALANCE XR-100WG (Work Group)
		
CSM 377		SCALANCE XC-100
		
		SCALANCE X108PoE
		
		SCALANCE X101-1
		
		SCALANCE X101-1LD

Highlights unmanaged Switches

- Industrial-grade design
- The right device type for each application
- Investment protection: existing networks can be extended with new products
- Wide range of usability in small or large networks, even outside the control cabinet
- Avoid additional training and introduction costs by using standardized Ethernet technology
- Versions for connection of twisted pair and fiber optic cables

MANAGED LAYER 2			MANAGED LAYER 2/3	
SCALANCE X-200 managed	SCALANCE X-200IRT managed	SCALANCE X-300 managed	SCALANCE X-400 managed Layer 2/3	SCALANCE X-500 managed Layer 3
For all network structures in machine-oriented applications up to linked units	Acting in hard real-time	Convincing performance – modular and powerful	Segmentation on all levels	Structuring high-performance plants and connecting them to the office IT
				
SCALANCE XF-200	SCALANCE X-200IRT	SCALANCE XC-/XCM-300	SCALANCE XC-400	SCALANCE XR-500
				
SCALANCE XB-200	SCALANCE XF-200BA IRT	SCALANCE XR-300	SCALANCE XM-400	SCALANCE XR-500WG (Work Group)
				
SCALANCE XC-200	SCALANCE X-200IRT PRO	SCALANCE XR-300WG (Work Group)	Port Extender	SCALANCE XR528-6M
				
SCALANCE XF-200BA		SCALANCE XR-300EEC		SCALANCE XR552-12M
				
SCALANCE XP-200				
				
SCALANCE X-200RNA				

Highlights managed Switches

- Real-time network (PROFINET and EtherNet/IP) and standard TCP/IP, eliminating of duplicate infrastructure
- High network availability due to integrated redundancy mechanisms and system redundancy
- Reduced downtimes by saving data for project planning and configuration
- Integration into existing concepts for network security through integrated security functions
- Configuration through WBM or CLI, local or remote
- Diagnostics through LEDs on the device, via WBM, or network management through SNMP with SINEC NMS
- Integration in the STEP 7 and PCS 7/PCS neo engineering tools
- Seamless system diagnostics with PROFINET
- High network and machine availability

Compact Switch Modules

More connection to SIMATIC

Compact switch modules (CSM) allow the easy and space-efficient integration of controls into existing Ethernet networks.

Applications

- For integration of small machines into existing automation networks
- Standalone operation of the machines
- For setting up small, local Ethernet networks

Variants

- LOGO! CSM**
- In LOGO! design
- CSM 1277**
- In SIMATIC S7-1200 design
- CSM 377**
- In SIMATIC S7-300 design

Highlights

- Transmission rate up to 100 Mbps
- Industrial-grade design, for example, retaining collars for PROFINET-compliant connector IE FC RJ45 Plug for additional strain relief

[siemens.com/csm](https://www.siemens.com/csm)

SCALANCE X-000/XB-000

Simple, space-saving, for industrial use

SCALANCE X-000/XB-000 switches are an affordable and easy entry-level solution for the realization of simple machine networks and small Ethernet networks.

Applications

- For setting up small industrial line or star structures in machine or plant sections
- For usage in rail and road traffic or building automation

Variants

- SCALANCE X005/X005EEC**
- 5 x RJ45-ports
 - Transmission rate up to 100 Mbps
- SCALANCE XB-000**
- Up to 8 x RJ45 ports/2 x SC
 - Transmission rate up to 1 Gbps
 - Variants with 24 V AC (50/60 Hz) for use in building automation

Highlights

- LED diagnostics on the device (power, link status, data traffic)
- Use of straight-through connecting cables thanks to integrated autocrossover function
- Automatic detection and negotiation of data rate

[siemens.com/x-000](https://www.siemens.com/x-000)

SCALANCE X-100

Full basic version for industrial use

SCALANCE X-100 switches are a cost-efficient solution for the setup of smaller networks.

Applications

- For setting up electrical and/or optical line and star structures in machine-oriented applications
- Power over Ethernet (PoE) if required

Variants

SCALANCE XB-100

- Up to 24 x RJ45 ports, 2 x SC, or ST/BFOC
- Transmission rate up to 100 Mbps
- PROFINET CC-A compliant

SCALANCE XR-100WG

- Small mounting depth for installing on both sides
- Up to 24 x RJ45 ports, 2 x SFP, of which 8 x RJ45 ports with PoE
- Transmission rate up to 10 Gbps

SCALANCE XC-100

- Transmission rate up to 100 Mbps
- Motor vehicle approval E1 (SCALANCE XC108 only)

SCALANCE X108PoE

- 8 x RJ45 ports, of which 2 x RJ45 with PoE
- Transmission rate up to 100 Mbps

Highlights

- LED diagnostics on the device (power, link status, data traffic)
- Use of straight-through connecting cables thanks to integrated autocrossover function
- Automatic detection and negotiation of data rate
- Work Group (WG) switches as affordable solution, available with PoE

[siemens.com/x-100](https://www.siemens.com/x-100)

UNMANAGED

SCALANCE X-100 Media Converter

Customized conversion

SCALANCE X-100 media converters transform electrical into optical signals and enable a cost-effective combination of copper and fiber optic cables in Industrial Ethernet networks.

Applications

- For integration of remote stations in glass fiber networks through fiber optic cables
- For bridging large distances

Variants

SCALANCE X101-1

- Implementation of 1 x 10/100 Mbps RJ45 to 1 x 100 Mbps ST/BFOC (multimode)
- Distances up to 5 kilometers

SCALANCE X101-1LD

- Implementation of 1 x 10/100 Mbps RJ45 to 1 x 100 Mbps ST/BFOC (single mode)
- Distances up to 26 kilometers

Highlights

- Transmission rate up to 100 Mbps
- LED diagnostics on the device (power, link status, data traffic)
- Redundant power supply

[siemens.com/x-100](https://www.siemens.com/x-100)

SCALANCE X-200

Universal and convenient

SCALANCE X-200 switches offer highest flexibility regarding handling thanks to their robust and compact construction with different port forms.

Applications

- For setting up Industrial Ethernet bus, star, and ring structures for high network availability and increased demand on functionality
- For machine-oriented applications and usage in the aggregation layer
- High bandwidth and Power over Ethernet (PoE) if required

- For small space requirements
- Mounting on rail / operating station with a retaining plate accessory (sold separately)
- Installation outside the control cabinet and outdoors
- For high temperatures, in harsh ambient conditions and hazardous areas
- Supply for PoE devices outside (e.g., WLAN Access Points)

- Seamless networks with HSR/PRP
- In process automation
- In energy supply systems
- For critical applications that require high availability with system redundancy

Variants

SCALANCE XF-200

- Up to 8 x RJ45/2 x ST/BFOC
- Distances up to 5 kilometers

SCALANCE XB-200

- Up to 13 x RJ45/3 x ST/BFOC or SC
- Distances up to 26 kilometers
- Console port
- For PROFINET and EtherNet/IP applications

SCALANCE XC-200

- Distances up to 200 km via SFPs
- Integrated diagnostics for fiber optic (Fiber Monitoring)
- For PROFINET and EtherNet/IP applications
- Trackage railway approval EN 50121-4

SCALANCE XF-200BA

- Up to 4 x RJ45/4 x SC RJ/4 x LC
- Flexible bus adapter concept
- For EtherNet/IP applications (SCALANCE XF204-2BA only)

SCALANCE XF204G

- Up to 4 x 10/100/1000 Mbps
- For PROFINET applications

SCALANCE XP-200

- Up to 16 x M12, of which 8 x PoE
- Up to 4 x 1 Gbps ports
- XP208G PP with AIDA push pull technology
- Support of redundancy mechanisms MRP, MRP Interconnection, and RSTP+
- Matching power supply SCALANCE PSP9230 PoE

SCALANCE X-200RNA

- Up to 4 x RJ45 ports/2 x FO
- Enables very short runtimes for network reconfiguration

Highlights

- Transmission rate up to 1000 Mbps
- Redundant power supply
- Increased plant availability due to integrated configuration and remote diagnostics

- Transmission rate up to 1 Gbps
- Redundant power supply
- Fast, redundant ring coupling with MRP Interconnection and RSTP+
- Support for VLANs (Virtual Local Area Network)

- Transmission rate up to 1 Gbps
- Redundant power supply

[siemens.com/x-200](https://www.siemens.com/x-200)

SCALANCE X-200IRT switches are specifically designed for tough real-time applications.

Applications	Variants	Highlights
<ul style="list-style-type: none"> • For high-speed Motion Control applications • For high-precision applications (isochronous mode) • For plant concepts without control cabinet 	<p>SCALANCE X-200IRT</p> <ul style="list-style-type: none"> • Up to 4 x RJ45/4 x ST/BFOC or SC RJ <p>SCALANCE XF-200BA IRT</p> <ul style="list-style-type: none"> • Flexible bus adapter concept • Up to 4 x RJ45 or 4 x SC RJ • 2 x bus adapter slots <p>SCALANCE X-200IRT PRO</p> <ul style="list-style-type: none"> • Up to 4 x RJ45/3 x SC RJ Push Pull 	<ul style="list-style-type: none"> • Transmission rate up to 100 Mbps • Support of PROFINET with IRT (Isochronous Real Time) requirements • Seamless redundancy (MRPD) for seamless switching • Redundant power supply <p style="text-align: right;">siemens.com/x-200</p>

SCALANCE X-300

Compact high performances

SCALANCE X-300 switches realize high-performing and flexible communication networks from OT to IT.

Applications	Variants	Highlights
<ul style="list-style-type: none"> • For large networks with high functionality and availability • High bandwidth and Power over Ethernet (PoE) if required 	<p>SCALANCE XC-/XCM-300</p> <ul style="list-style-type: none"> • Up to 32 x RJ45 • Transmission rate of up to 10 Gbps • Distances up to 100 kilometers <p>SCALANCE XR-300WG</p> <ul style="list-style-type: none"> • Small mounting depth for installing on both sides in 19" control cabinets • Up to 24 x RJ45 ports, 4 x combo ports (up to 24 x 1 Gbps RJ45 PoE) • Transmission rate of up to 1 Gbps • Support of redundancy mechanisms MRP, MRP Interconnection and RSTP+ 	<ul style="list-style-type: none"> • Support of VLANs • Redundant power supply • Work Group (WG) switches as affordable variants, available with PoE • Easy connection to SCALANCE LPE local processing engine via function extender interface
<p>Accessories</p> <p>Plug-in transceivers, and PoE power supply</p>	<p>SCALANCE XR-300/XRM-300</p> <ul style="list-style-type: none"> • Variants with 8, 12 or 32 FO ports • Transmission rate of up to 10 Gbps • Support of redundancy mechanisms MRP, HSR, PRP <p>SCALANCE XR326-800EEC/XRH-334</p> <ul style="list-style-type: none"> • Variants with 8 FO ports • Transmission rate of up to 10 Gbps • For rough environmental conditions 	<p style="text-align: right;">siemens.de/x-300</p>

SCALANCE X-400

Secure connection of plants via network segmentation

SCALANCE X-400 router offer more flexibility thanks to a high number of ports and the support of different transmission media.

Applications

- For high-performance plant networks
- Network security through segmentation
- For communication in layer 2 or layer 3 networks
- Power over Ethernet (PoE) if required

Accessories

Power Supplies

- 54 V DC power supply for Power over Ethernet according to IEEE 802.3at
- High power for connected end devices possible (up to 30 watts)

Plug-in transceivers

- Optical connection to cables with LC connectors
- Use in combination with SCALANCE XM408-8C, XM416-4C, and PE400-8SFP

Variants

SCALANCE XC-400

- max. 32 x RJ45 ports with 1000 Mbps or max. 4 x SFP+ ports with 10 Gbps

SCALANCE XM-400

- 8 x or 16 x RJ45 ports
- Can be extended up to 24 x ports (with port and function extender)
- Transmission rate up to 1 Gbps

Port Extender

- 8 x RJ45 ports with PE408
- 8 x RJ45 ports with PoE with PE408 PoE
- 8 x SFP slots with PE400-8SFP

Highlights

- Modular expandable
- Optional connection of layer 3 functionality
- Support of VLANs
- Console port
- Redundant power supply

[siemens.com/x-400](https://www.siemens.com/x-400)

SCALANCE X-500

High-performance integration of machines into the company IT

SCALANCE X-500 router are the central component for a high-performing network and are available as 19" model with different height units.

Applications	Variants	Highlights
<ul style="list-style-type: none"> • For structuring high-speed production networks with connection to the enterprise IT • Network security through segmentation • For transmission of high data rates (10 Gbps) • Communication in layer 2 or layer 3 networks 	<p>SCALANCE XR526-8</p> <ul style="list-style-type: none"> • For large quantity structures with 34 ports, incl. 8 FO and 26 RJ45 ports <p>SCALANCE XR522-12</p> <ul style="list-style-type: none"> • For large quantity structures with 34 ports, incl. 12 FO and 22 RJ45 ports <p>SCALANCE XR502-32</p> <ul style="list-style-type: none"> • For large quantity structures with 34 ports, incl. 32 FO and 2 RJ45 ports <p>SCALANCE XR524-8C</p> <ul style="list-style-type: none"> • For large scales with 28 ports <p>SCALANCE XR524-8WG</p> <ul style="list-style-type: none"> • 32 ports, incl. 8 FO ports • Cost-efficient star distributor <p>SCALANCE XR526-8C</p> <ul style="list-style-type: none"> • For large scales with 26 ports <p>SCALANCE XR528-6M</p> <ul style="list-style-type: none"> • For large scales with 28 ports • Up to 6 x 4-port media modules for electrical and optical connections <p>SCALANCE XR552-12M</p> <ul style="list-style-type: none"> • For very large scales with 52 ports • Up to 12 x 4-port media modules for electrical and optical connections 	<ul style="list-style-type: none"> • Support of VLANs • Modular with media modules or SFP and SFP+ plug-in transceivers • Redundant power supply • Console port • Granular network extension to 10 Gbps during operation <p style="text-align: right;">siemens.com/x-500</p>
<p>Accessories</p> <p>Media modules</p> <ul style="list-style-type: none"> • Electrical and optical variants • 4-port media modules • Use for SCALANCE XR552-12M and XR528-6M <p>Plug-in transceivers</p> <ul style="list-style-type: none"> • SFP plug-in transceiver with transmission rates up to 100 or 1000 Mbps • SFP+ plug-in transceiver with 10 Gbps • Optical connection to cables with LC connectors 		

Siemens AG

Process Industries and Drives Division
Process Automation
Postfach 48 48
90026 Nürnberg
Germany

© Siemens AG 2024

Subject to change without prior notice.

PDF (6ZB5530-1AN02-0BB5)

BR 0524 12 En

Printed in Germany

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract. Availability and technical specifications are subject to change without notice.

All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.

Security-Hinweise

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, systems, machines and networks.

In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial security concept. Siemens' products and solutions constitute one element of such a concept.

Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place.

For additional information on industrial security measures that may be implemented, please visit [siemens.com/industrialsecurity](https://www.siemens.com/industrialsecurity).

Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats.

To stay informed about product updates, subscribe to the Siemens Industrial Security RSS Feed under [siemens.com/industrialsecurity](https://www.siemens.com/industrialsecurity).