

UK Declaration of Conformity

No. 666.MNERo.BG.40.2306.004

Manufacturer: Siemens AG, DI MC
Address: Frauenaauracher Straße 80
91056 Erlangen
Germany

UK importer: Siemens plc
UK importer address: Manchester
M20 2UR
United Kingdom

Product Family: SINAMICS S120

The indicated product family placed on the market by us is in conformance to the regulations of the following UK Regulations:

Supply of Machinery (Safety) Regulations 2008

+ Related amendments

More details regarding adherence to this Regulation is provided in Appendix MD.

Electrical Equipment (Safety) Regulations 2016

+ Notice of Publication 0009/21

More details regarding adherence to this Regulation is provided in Appendix LVD.

Electromagnetic Compatibility Regulations 2016

+ Notice of Publication 0007/21

More details regarding adherence to this Regulation is provided in Appendix EMC.

The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012

+ Notice of Publication 0037/21

More details regarding adherence to this Regulation is provided in Appendix RoHS.

This declaration of conformity is issued under the sole responsibility of the manufacturer.

Erlangen, 23-06-21

X 

i.V. D. Vielsäcker
Head of Test, Processes & Architecture
Signiert von: Vielsaecker Dirk

X 

i.V. A. Schöppler
Head of Quality Management & EHS
Signiert von: Schoeppler Andreas

Appendix MD

to UK Declaration of Conformity

No. 666.MNERo.BG.40.2306.004

Product family: **SINAMICS S120**

Conformity of the products designated below with the Supply of Machinery (Safety) Regulations 2008 is verified by adherence to the following standards.

Reference number: **Edition:**

EN 61800-5-2 **2017**

This standard implicitly includes the related product standard EN 61800-5-1 for all modules listed under Machinery Directive that are also subject to the Low Voltage Regulation.

The person authorized to compile the technical documents is the responsible Functional Safety Manager of Siemens AG, DI MC.

The components of the product family to which the UK marking applies are given in the Appendix "Component List".

Appendix LVD

to UK Declaration of Conformity

No. 666.MNERo.BG.40.2306.004

Product family: **SINAMICS S120**

Conformity of the products designated below with the Electrical Equipment (Safety) Regulations 2016 is verified by adherence to the following standards:

Reference number: **Edition:**

EN 61800-5-1 **2007+A1:2017**

EN 61800-5-1 **2007+A11:2021**

The components of the product family to which the UK marking applies are given in the Appendix "Component List".

Appendix EMC

to UK Declaration of Conformity

No. 666.MNERo.BG.40.2306.004

Product family: **SINAMICS S120**

Conformity of the products designated below with the Electromagnetic Compatibility Regulations 2016 is verified by adherence to the following standards:

Reference number: **Edition:**

EN IEC 61800-3 **2004+A1:2012**

The components of the product family to which the UK marking applies are given in the Appendix "Component List".

Appendix RoHS

to UK Declaration of Conformity

No. 666.MNERo.BG.40.2306.004

Product family: **SINAMICS S120**

Conformity of the products designated below with the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 is verified by adherence to the following standards:

Reference number: **Edition:**

EN IEC 63000 **2018**

The components of the product family to which the UK marking applies are given in the Appendix "Component List".

Appendix Component List to UK Declaration of Conformity

No. 666.MNERo.BG.40.2306.004

The compliance of the designated product family modules with the requirements of the applied regulations and directives is indicated by "x".

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
Control Units						
CU310 DP	6SL3040-0LA00-0AA0	CONTROL UNIT	x	---	x	---
CU310 DP	6SL3040-0LA00-0AA1	CONTROL UNIT	x	---	x	---
CU310 PN	6SL3040-0LA01-0AA1	CONTROL UNIT	x	---	x	---
CU320	6SL3040-0MA00-0AA1	CONTROL UNIT	x	---	x	---
CUA31	6SL3040-0PA00-0AA1	CONTROL UNIT	x	---	x	x
CUA32	6SL3040-0PA01-0AA0	CONTROL UNIT	x	---	x	x
CU310-2 DP	6SL3040-1LA00-0AA0	CONTROL UNIT	x	---	x	x
CU310-2 PN	6SL3040-1LA01-0AA0	CONTROL UNIT	x	---	x	x
CU320-2 DP	6SL3040-1MA00-0AA0	CONTROL UNIT	x	---	x	x
CU320-2 PN	6SL3040-1MA01-0AA0	CONTROL UNIT	x	---	x	x
CUA20	6SL3255-0BW01-0NA0	OPTION MODULE	x	---	x	x
Basic Line Modules						
BLM (380-480V, 20kW, INT)	6SL3130-1TE22-0AA0	CONVERTER	---	x	x	x
BLM (380-480V, 40kW, INT)	6SL3130-1TE24-0AA0	CONVERTER	---	x	x	x
BLM (380-480V, 100kW, INT)	6SL3130-1TE31-0AA0	CONVERTER	---	x	x	x
BLM (380-480V, 20kW, COL)	6SL3136-1TE22-0AA0	CONVERTER	---	x	x	x
BLM (380-480V, 40kW, COL)	6SL3136-1TE24-0AA0	CONVERTER	---	x	x	x
BLM (380-480V, 100kW, COL)	6SL3136-1TE31-0AA0	CONVERTER	---	x	x	x
BLM (380-480V, 200kW, INT, Chassis)	6SL3330-1TE34-2AA0	CONVERTER	---	x	x	---
BLM (380-480V, 200kW, INT, Chassis)	6SL3330-1TE34-2AA3	CONVERTER	---	x	x	x
BLM (380-480V, 250kW, INT, Chassis)	6SL3330-1TE35-3AA0	CONVERTER	---	x	x	---
BLM (380-480V, 250kW, INT, Chassis)	6SL3330-1TE35-3AA3	CONVERTER	---	x	x	x
BLM (380-480V, 400kW, INT, Chassis)	6SL3330-1TE38-2AA3	CONVERTER	---	x	x	x
BLM (380-480V, 560kW, INT, Chassis)	6SL3330-1TE41-2AA3	CONVERTER	---	x	x	x
BLM (380-480V, 710kW, INT, Chassis)	6SL3330-1TE41-5AA3	CONVERTER	---	x	x	x
BLM (380-480V, 900kW, INT, Chassis)	6SL3330-1TE41-8AA3	CONVERTER	---	x	x	x
BLM (500-690V, 250kW, INT, Chassis)	6SL3330-1TG33-0AA3	CONVERTER	---	x	x	x
BLM (500-690V, 355kW, INT, Chassis)	6SL3330-1TG34-3AA3	CONVERTER	---	x	x	x
BLM (500-690V, 560kW, INT, Chassis)	6SL3330-1TG36-8AA3	CONVERTER	---	x	x	x
BLM (500-690V, 900kW, INT, Chassis)	6SL3330-1TG41-1AA3	CONVERTER	---	x	x	x
BLM (500-690V, 1100kW, INT, Chassis)	6SL3330-1TG41-4AA3	CONVERTER	---	x	x	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The compliance of the designated product family modules with the requirements of the applied regulations and directives is indicated by "x".

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
BLM (500-690V, 1500kW, INT, Chassis)	6SL3330-1TG41-8AA3	CONVERTER	---	x	x	x
BLM (500-690V, 250kW, INT, Chassis)	6SL3330-1TH33-0AA0	CONVERTER	---	x	x	---
BLM (380-480V, 360kW, LC, Chassis)	6SL3335-1TE37-4AA3	CONVERTER	---	x	x	x
BLM (380-480V, 600kW, LC, Chassis)	6SL3335-1TE41-2AA3	CONVERTER	---	x	x	x
BLM (380-480V, 830kW, LC, Chassis)	6SL3335-1TE41-7AA3	CONVERTER	---	x	x	x
BLM (500-690V, 355kW, LC, Chassis)	6SL3335-1TG34-2AA3	CONVERTER	---	x	x	x
BLM (500-690V, 630kW, LC, Chassis)	6SL3335-1TG37-3AA3	CONVERTER	---	x	x	x
BLM (500-690V, 1100kW, LC, Chassis)	6SL3335-1TG41-3AA3	CONVERTER	---	x	x	x
BLM (500-690V, 1370kW, LC, Chassis)	6SL3335-1TG41-7AA3	CONVERTER	---	x	x	x
Smart Line Modules						
SLM (380-480V, 5kW, INT)	6SL3130-6AE15-0AB1	CONVERTER	---	x	x	x
SLM (380-480V, 10kW, INT)	6SL3130-6AE21-0AA0	CONVERTER	---	x	x	---
SLM (380-480V, 10kW, INT)	6SL3130-6AE21-0AB1	CONVERTER	---	x	x	x
SLM (380-480V, 16kW, INT)	6SL3130-6TE21-6AA3	CONVERTER	---	x	x	---
SLM (380-480V, 16kW, INT)	6SL3130-6TE21-6AA4	CONVERTER	---	x	x	x
SLM (380-480V, 16kW, INT)	6SL3130-6TE21-6AB0	CONVERTER	---	x	x	---
SLM (380-480V, 36kW, INT)	6SL3130-6TE23-6AA3	CONVERTER	---	x	x	x
SLM (380-480V, 36kW, INT)	6SL3130-6TE23-6AB0	CONVERTER	---	x	x	---
SLM /380-480V, 55kW, INT)	6SL3130-6TE25-5AA3	CONVERTER	---	x	x	x
SLM (380-480V, 5kW, EXT)	6SL3131-6AE15-0AA1	CONVERTER	---	x	x	x
SLM (380-480V, 10kW, EXT)	6SL3131-6AE21-0AA1	CONVERTER	---	x	x	x
SLM (380-480V, 16kW, EXT)	6SL3131-6TE21-6AA3	CONVERTER	---	x	x	x
SLM (380-480V, 36kW, EXT)	6SL3131-6TE23-6AA3	CONVERTER	---	x	x	x
SLM (380-480V, 55kW, EXT)	6SL3131-6TE25-5AA3	CONVERTER	---	x	x	x
SLM (380-480V, 5kW, COL)	6SL3136-6AE15-0AA0	CONVERTER	---	x	x	---
SLM (380-480V, 5kW, COL)	6SL3136-6AE15-0AA1	CONVERTER	---	x	x	x
SLM (380-480V, 10kW, COL)	6SL3136-6AE21-0AA0	CONVERTER	---	x	x	---
SLM (380-480V, 10kW, COL)	6SL3136-6AE21-0AA1	CONVERTER	---	x	x	x
SLM (380-480V, I250kW, INT, Chassis)	6SL3330-6TE35-5AA3	CONVERTER	---	x	x	x
SLM (380-480V, I355kW, INT, Chassis)	6SL3330-6TE37-3AA3	CONVERTER	---	x	x	x
SLM (380-480V, 500kW, INT, Chassis)	6SL3330-6TE41-1AA3	CONVERTER	---	x	x	x
SLM (380-480V, 630kW, INT, Chassis)	6SL3330-6TE41-3AA3	CONVERTER	---	x	x	x
SLM (380-480V, 800kW, INT, Chassis)	6SL3330-6TE41-7AA3	CONVERTER	---	x	x	x
SLM (500-690V, 450kW, INT, Chassis)	6SL3330-6TG35-5AA3	CONVERTER	---	x	x	x
SLM (500-690V, 710kW, INT, Chassis)	6SL3330-6TG38-8AA0	CONVERTER	---	x	x	x
SLM (500-690V, 710kW, INT, Chassis)	6SL3330-6TG38-8AA3	CONVERTER	---	x	x	x
SLM (500-690V, 1000kW, INT, Chassis)	6SL3330-6TG41-2AA0	CONVERTER	---	x	x	x
SLM (500-690V, 1000kW, INT, Chassis)	6SL3330-6TG41-2AA3	CONVERTER	---	x	x	x
SLM (500-690V, 1400kW, INT, Chassis)	6SL3330-6TG41-7AA3	CONVERTER	---	x	x	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The compliance of the designated product family modules with the requirements of the applied regulations and directives is indicated by "x".

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
SLM (380-480V, 16kW, INT, Compact)	6SL3430-6TE21-6AA1	CONVERTER	---	x	x	x
Active Line Modules						
ALM (380-480V, 16kW, INT)	6SL3130-7TE21-6AA0	CONVERTER	---	x	x	---
ALM (380-480V, 16kW, INT)	6SL3130-7TE21-6AA1	CONVERTER	---	x	x	---
ALM (380-480V, 16kW, INT)	6SL3130-7TE21-6AA3	CONVERTER	---	x	x	---
ALM (380-480V, 16kW, INT)	6SL3130-7TE21-6AA4	CONVERTER	---	x	x	x
ALM (380-480V, 16kW, INT)	6SL3130-7TE21-6AB0	CONVERTER	---	x	x	---
ALM (380-480V, 36kW, INT)	6SL3130-7TE23-6AA0	CONVERTER	---	x	x	---
ALM (380-480V, 36kW, INT)	6SL3130-7TE23-6AA1	CONVERTER	---	x	x	---
ALM (380-480V, 36kW, INT)	6SL3130-7TE23-6AA3	CONVERTER	---	x	x	x
ALM (380-480V, 36kW, INT)	6SL3130-7TE23-6AB0	CONVERTER	---	x	x	---
ALM (380-480V, 55kW, INT)	6SL3130-7TE25-5AA0	CONVERTER	---	x	x	---
ALM (380-480V, 55kW, INT)	6SL3130-7TE25-5AA1	CONVERTER	---	x	x	---
ALM (380-480V, 55kW, INT)	6SL3130-7TE25-5AA3	CONVERTER	---	x	x	x
ALM (380-480V, 55kW, INT)	6SL3130-7TE25-5AB0	CONVERTER	---	x	x	---
ALM (380-480V, 80kW, INT)	6SL3130-7TE28-0AA1	CONVERTER	---	x	x	---
ALM (380-480V, 80kW, INT)	6SL3130-7TE28-0AA3	CONVERTER	---	x	x	x
ALM (380-480V, 80kW, INT)	6SL3130-7TE28-0AB0	CONVERTER	---	x	x	---
ALM (380-480V, 120kW, INT)	6SL3130-7TE31-2AA1	CONVERTER	---	x	x	---
ALM (380-480V, 120kW, INT)	6SL3130-7TE31-2AA3	CONVERTER	---	x	x	x
ALM (380-480V, 120kW, INT)	6SL3130-7TE31-2AB0	CONVERTER	---	x	x	---
ALM (380-480V, 16kW, EXT)	6SL3131-7TE21-6AA0	CONVERTER	---	x	x	---
ALM (380-480V, 16kW, EXT)	6SL3131-7TE21-6AA3	CONVERTER	---	x	x	---
ALM (380-480V, 36kW, EXT)	6SL3131-7TE23-6AA0	CONVERTER	---	x	x	---
ALM (380-480V, 36kW, EXT)	6SL3131-7TE23-6AA3	CONVERTER	---	x	x	---
ALM (380-480V, 55kW, EXT)	6SL3131-7TE25-5AA0	CONVERTER	---	x	x	---
ALM (380-480V, 55kW, EXT)	6SL3131-7TE25-5AA3	CONVERTER	---	x	x	---
ALM (380-480V, 80kW, EXT)	6SL3131-7TE28-0AA0	CONVERTER	---	x	x	---
ALM (380-480V, 80kW, EXT)	6SL3131-7TE28-0AA3	CONVERTER	---	x	x	---
ALM (380-480V, 120kW, EXT)	6SL3131-7TE31-2AA0	CONVERTER	---	x	x	---
ALM (380-480V, 120kW, EXT)	6SL3131-7TE31-2AA3	CONVERTER	---	x	x	---
ALM (380-480V, 120kW, LC)	6SL3135-7TE31-2AA3	CONVERTER	---	x	x	---
ALM (380-480V, 16kW, COL)	6SL3136-7TE21-6AA0	CONVERTER	---	x	x	---
ALM (380-480V, 16kW, COL)	6SL3136-7TE21-6AA3	CONVERTER	---	x	x	x
ALM (380-480V, 36kW, COL)	6SL3136-7TE23-6AA0	CONVERTER	---	x	x	---
ALM (380-480V, 36kW, COL)	6SL3136-7TE23-6AA3	CONVERTER	---	x	x	x
ALM (380-480V, 55kW, COL)	6SL3136-7TE25-5AA0	CONVERTER	---	x	x	---
ALM (380-480V, 55kW, COL)	6SL3136-7TE25-5AA1	CONVERTER	---	x	x	---
ALM (380-480V, 55kW, COL)	6SL3136-7TE25-5AA3	CONVERTER	---	x	x	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The compliance of the designated product family modules with the requirements of the applied regulations and directives is indicated by "x".

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
ALM (380-480V, 80kW, COL)	6SL3136-7TE28-0AA1	CONVERTER	---	x	x	---
ALM (380-480V, 80kW, COL)	6SL3136-7TE28-0AA3	CONVERTER	---	x	x	x
ALM (380-480V, 120kW, COL)	6SL3136-7TE31-2AA1	CONVERTER	---	x	x	---
ALM (380-480V, 120kW, COL)	6SL3136-7TE31-2AA3	CONVERTER	---	x	x	x
ALM (380-480V, 132kW, INT, Chassis)	6SL3330-7TE32-1AA0	CONVERTER	---	x	x	---
ALM (380-480V, 132kW, INT, Chassis)	6SL3330-7TE32-1AA3	CONVERTER	---	x	x	x
ALM (380-480V, 132kW, INT, EB)	6SL3330-7TE32-1AB3	SPARE PART	---	x	x	x
ALM (380-480V, 160kW, INT, Chassis)	6SL3330-7TE32-6AA0	CONVERTER	---	x	x	---
ALM (380-480V, 160kW, INT, Chassis)	6SL3330-7TE32-6AA3	CONVERTER	---	x	x	x
ALM (380-480V, 160kW, INT, EB)	6SL3330-7TE32-6AB3	SPARE PART	---	x	x	x
ALM (380-480V, 235kW, INT, Chassis)	6SL3330-7TE33-8AA0	CONVERTER	---	x	x	---
ALM (380-480V, 235kW, INT, Chassis)	6SL3330-7TE33-8AA3	CONVERTER	---	x	x	x
ALM (380-480V, 235kW, INT, EB)	6SL3330-7TE33-8AB3	SPARE PART	---	x	x	x
ALM (380-480V, 300kW, INT, Chassis)	6SL3330-7TE35-0AA0	CONVERTER	---	x	x	---
ALM (380-480V, 300kW, INT, Chassis)	6SL3330-7TE35-0AA3	CONVERTER	---	x	x	x
ALM (380-480V, 300kW, INT, Chassis)	6SL3330-7TE35-0AA4	CONVERTER	---	x	x	x
ALM (380-480V, 300kW, INT, EB)	6SL3330-7TE35-0AB3	SPARE PART	---	x	x	x
ALM (380-480V, 380kW, INT, Chassis)	6SL3330-7TE36-1AA3	CONVERTER	---	x	x	x
ALM (380-480V, 450kW, INT, Chassis)	6SL3330-7TE37-5AA3	CONVERTER	---	x	x	x
ALM (380-480V, 500kW, INT, Chassis)	6SL3330-7TE38-4AA3	CONVERTER	---	x	x	x
ALM (380-480V, 630kW, INT, Chassis)	6SL3330-7TE41-0AA3	CONVERTER	---	x	x	x
ALM (380-480V, 630kW, INT, Chassis)	6SL3330-7TE41-0AA4	CONVERTER	---	x	x	x
ALM (380-480V, 800kW, INT, Chassis)	6SL3330-7TE41-2AA3	CONVERTER	---	x	x	x
ALM (380-480V, 900kW, INT, Chassis)	6SL3330-7TE41-4AA3	CONVERTER	---	x	x	x
ALM (380-480V, 900kW, INT, Chassis)	6SL3330-7TE41-4AA4	CONVERTER	---	x	x	x
ALM (500-690V, 150kW, INT, EB)	6SL3330-7TG31-4AB3	SPARE PART	---	x	x	x
ALM (500-690V, 330kW, INT, EB)	6SL3330-7TG33-1AB3	SPARE PART	---	x	x	x
ALM (500-690V, 630kW, INT, Chassis)	6SL3330-7TG35-8AA3	CONVERTER	---	x	x	x
ALM (500-690V, 800kW, INT, Chassis)	6SL3330-7TG37-4AA3	CONVERTER	---	x	x	x
ALM (500-690V, 1100kW, INT, Chassis)	6SL3330-7TG41-0AA3	CONVERTER	---	x	x	x
ALM (500-690V, 1100kW, INT, Chassis)	6SL3330-7TG41-0AA4	CONVERTER	---	x	x	x
ALM (500-690V, 1400kW, INT, Chassis)	6SL3330-7TG41-3AA3	CONVERTER	---	x	x	x
ALM (500-690V, 1400kW, INT, Chassis)	6SL3330-7TG41-3AA4	CONVERTER	---	x	x	x
ALM (380-480V, 355kW, INT, Chassis)	6SL3331-7TE35-6AA0	CONVERTER	---	x	x	x
ALM (380-480V, 400kW, INT, Chassis)	6SL3331-7TE36-4AA0	CONVERTER	---	x	x	x
ALM (380-480V, 450kW, INT, Chassis)	6SL3331-7TE37-5AA0	CONVERTER	---	x	x	x
ALM (380-480V, 500kW, INT, Chassis)	6SL3331-7TE38-4AA0	CONVERTER	---	x	x	x
ALM (380-480V, 560kW, INT, Chassis)	6SL3331-7TE38-8AA0	CONVERTER	---	x	x	x
ALM (380-480V, 630kW, INT, Chassis)	6SL3331-7TE41-0AA0	CONVERTER	---	x	x	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The compliance of the designated product family modules with the requirements of the applied regulations and directives is indicated by "x".

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
ALM (380-480V, 710kW, INT, Chassis)	6SL3331-7TE41-2AA0	CONVERTER	---	x	x	x
ALM (380-480V, 800kW, INT, Chassis)	6SL3331-7TE41-3AA0	CONVERTER	---	x	x	x
ALM (380-480V, 900kW, INT, Chassis)	6SL3331-7TE41-4AA0	CONVERTER	---	x	x	x
ALM (380-480V, 300kW, LC, Chassis)	6SL3335-7TE35-0AA3	CONVERTER	---	x	x	x
ALM (380-480V, 380kW, LC, Chassis)	6SL3335-7TE36-1AA3	CONVERTER	---	x	x	x
ALM (380-480V, 500kW, LC, Chassis)	6SL3335-7TE38-4AA3	CONVERTER	---	x	x	x
ALM (380-480V, 630kW, LC, Chassis)	6SL3335-7TE41-0AA3	CONVERTER	---	x	x	x
ALM (380-480V, 630kW, LC, Chassis)	6SL3335-7TE41-0AA7	CONVERTER	---	x	x	x
ALM (380-480V, 900kW, LC, Chassis)	6SL3335-7TE41-4AA3	CONVERTER	---	x	x	x
ALM (380-480V, 900kW, LC, Chassis)	6SL3335-7TE41-4AA7	CONVERTER	---	x	x	x
ALM (500-690V, 630kW, LC, Chassis)	6SL3335-7TG35-8AA3	CONVERTER	---	x	x	x
ALM (500-690V, 630kW, LC, Chassis)	6SL3335-7TG35-8AA4	CONVERTER	---	x	x	x
ALM (500-690V, 630kW, LC, Chassis)	6SL3335-7TG35-8AA7	CONVERTER	---	x	x	x
ALM (500-690V, 630kW, LC, Chassis)	6SL3335-7TG35-8AA8	CONVERTER	---	x	x	x
ALM (500-690V, 800kW, LC, Chassis)	6SL3335-7TG37-4AA3	CONVERTER	---	x	x	x
ALM (500-690V, 900kW, LC, Chassis)	6SL3335-7TG38-1AA3	CONVERTER	---	x	x	x
ALM (500-690V, 900kW, LC, Chassis)	6SL3335-7TG38-1AA7	CONVERTER	---	x	x	x
ALM (500-690V, 1100kW, LC, Chassis)	6SL3335-7TG41-0AA3	CONVERTER	---	x	x	x
ALM (500-690V, 1100kW, LC, Chassis)	6SL3335-7TG41-0AA7	CONVERTER	---	x	x	x
ALM (500-690V, 1400kW, LC, Chassis)	6SL3335-7TG41-3AA3	CONVERTER	---	x	x	x
ALM (500-690V, 1400kW, LC, Chassis)	6SL3335-7TG41-3AA4	CONVERTER	---	x	x	x
ALM (500-690V, 1400kW, LC, Chassis)	6SL3335-7TG41-3AA7	CONVERTER	---	x	x	x
ALM (500-690V, 1400kW, LC, Chassis)	6SL3335-7TG41-3AA8	CONVERTER	---	x	x	x
ALM (500-690V, 1700kW, LC, Chassis)	6SL3335-7TG41-6AA3	CONVERTER	---	x	x	x
ALM (500-690V, 1700kW, LC, Chassis)	6SL3335-7TG41-6AA4	CONVERTER	---	x	x	x
ALM (500-690V, 1700kW, LC, Chassis)	6SL3335-7TG41-6AA7	CONVERTER	---	x	x	x
ALM (500-690V, 1700kW, LC, Chassis)	6SL3335-7TG41-6AA8	CONVERTER	---	x	x	x
ALM (380-480V, 400kW, INT, EB)	6SL3355-7TE37-4AA0	SPARE PART	---	x	x	x
ALM (380-480V, 500kW, INT, EB)	6SL3355-7TE38-4AA0	SPARE PART	---	x	x	x
ALM (380-480V, 710kW, INT, EB)	6SL3355-7TE41-2AA0	SPARE PART	---	x	x	x
ALM (380-480V, 900kW, INT, EB)	6SL3355-7TE41-4AA0	SPARE PART	---	x	x	x
Diode Line Module						
DLM (6 pulse, 690V, 1300A, 1100kW, LC)	6SL3335-1AG41-3AA1	CONVERTER	---	x	---	x
DLM (6 pulse, 690V, 2000A, 1830kW, LC)	6SL3335-1AG42-0AA7	CONVERTER	---	x	---	x
DLM (6 pulse, 690V, 2600A, 2200kW, LC)	6SL3335-1AG42-6AA1	CONVERTER	---	x	---	x
DLM (12 pulse, 690V, 2x1000A, 2x915kW, LC)	6SL3335-2AG42-0AA7	CONVERTER	---	x	---	x
Single Motor Modules						
SMM (380-480V, 3A, INT)	6SL3120-1TE13-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 3A, INT)	6SL3120-1TE13-0AA4	MOTOR MODULE	x	---	x	---

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The compliance of the designated product family modules with the requirements of the applied regulations and directives is indicated by "x".

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
SMM (380-480V, 3A, INT)	6SL3120-1TE13-0AD0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 3A, INT)	6SL3120-1TE13-0AD7	MOTOR MODULE	x	---	x	x
SMM (380-480V, 5A, INT)	6SL3120-1TE15-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 5A, INT)	6SL3120-1TE15-0AA4	MOTOR MODULE	x	---	x	---
SMM (380-480V, 5A, INT)	6SL3120-1TE15-0AD0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 5A, INT)	6SL3120-1TE15-0AD7	MOTOR MODULE	x	---	x	x
SMM (380-480V, 9A, INT)	6SL3120-1TE21-0AA1	MOTOR MODULE	x	---	x	---
SMM (380-480V, 9A, INT)	6SL3120-1TE21-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 9A, INT)	6SL3120-1TE21-0AA4	MOTOR MODULE	x	---	x	---
SMM (380-480V, 9A, INT)	6SL3120-1TE21-0AD0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 9A, INT)	6SL3120-1TE21-0AD7	MOTOR MODULE	x	---	x	x
SMM (380-480V, 18A, INT)	6SL3120-1TE21-8AA1	MOTOR MODULE	x	---	x	---
SMM (380-480V, 18A, INT)	6SL3120-1TE21-8AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 18A, INT)	6SL3120-1TE21-8AA4	MOTOR MODULE	x	---	x	---
SMM (380-480V, 18A, INT)	6SL3120-1TE21-8AC0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 18A, INT)	6SL3120-1TE21-8AC7	MOTOR MODULE	x	---	x	x
SMM (380-480V, 18A, INT)	6SL3120-1TE21-8AD0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 18A, INT)	6SL3120-1TE21-8AD7	MOTOR MODULE	x	---	x	x
SMM (380-480V, 24A, INT)	6SL3120-1TE22-4AC0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 24A, INT)	6SL3120-1TE22-4AD0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 30A, INT)	6SL3120-1TE23-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 30A, INT)	6SL3120-1TE23-0AA4	MOTOR MODULE	x	---	x	---
SMM (380-480V, 30A, INT)	6SL3120-1TE23-0AC0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 30A, INT)	6SL3120-1TE23-0AD0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 45A, INT)	6SL3120-1TE24-5AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 45A, INT)	6SL3120-1TE24-5AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 45A, INT)	6SL3120-1TE24-5AC0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 60A, INT)	6SL3120-1TE26-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 60A, INT)	6SL3120-1TE26-0AC0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 85A, INT)	6SL3120-1TE28-5AA1	MOTOR MODULE	x	---	x	---
SMM (380-480V, 85A, INT)	6SL3120-1TE28-5AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 132A, INT)	6SL3120-1TE31-3AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 200A, INT)	6SL3120-1TE32-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 200A, INT)	6SL3120-1TE32-0AA4	MOTOR MODULE	x	---	x	x
SMM (380-480V, 24A, INT)	6SL3120-1UE22-4AD0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 30A, INT)	6SL3120-1UE23-0AD0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 60A, INT)	6SL3120-1UE26-0AC0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 9A, INT)	6SL3120-1VE21-0AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 18A, INT)	6SL3120-1VE21-8AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 24A, INT)	6SL3120-1VE22-4AA0	MOTOR MODULE	x	---	x	---

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The compliance of the designated product family modules with the requirements of the applied regulations and directives is indicated by "x".

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
SMM (380-480V, 3A, EXT)	6SL3121-1TE13-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 3A, EXT)	6SL3121-1TE13-0AA4	MOTOR MODULE	x	---	x	---
SMM (380-480V, 5A, EXT)	6SL3121-1TE15-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 5A, EXT)	6SL3121-1TE15-0AA4	MOTOR MODULE	x	---	x	---
SMM (380-480V, 9A, EXT)	6SL3121-1TE21-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 9A, EXT)	6SL3121-1TE21-0AA4	MOTOR MODULE	x	---	x	---
SMM (380-480V, 18A, EXT)	6SL3121-1TE21-8AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 18A, EXT)	6SL3121-1TE21-8AA4	MOTOR MODULE	x	---	x	---
SMM (380-480V, 30A, EXT)	6SL3121-1TE23-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 45A, EXT)	6SL3121-1TE24-5AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 60A, EXT)	6SL3121-1TE26-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 85A, EXT)	6SL3121-1TE28-5AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 132A, EXT)	6SL3121-1TE31-3AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 132A, EXT)	6SL3121-1TE31-3AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 200A, EXT)	6SL3121-1TE32-0AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 200A, EXT)	6SL3121-1TE32-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 200A, EXT)	6SL3121-1TE32-0AA4	MOTOR MODULE	x	---	x	---
SMM (380-480V, 200A, LC)	6SL3125-1TE32-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 200A, LC)	6SL3125-1TE32-0AA4	MOTOR MODULE	x	---	x	---
SMM (380-480V, 3A, COL)	6SL3126-1TE13-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 3A, COL)	6SL3126-1TE13-0AA4	MOTOR MODULE	x	---	x	x
SMM (380-480V, 5A, COL)	6SL3126-1TE15-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 5A, COL)	6SL3126-1TE15-0AA4	MOTOR MODULE	x	---	x	x
SMM (380-480V, 9A, COL)	6SL3126-1TE21-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 9A, COL)	6SL3126-1TE21-0AA4	MOTOR MODULE	x	---	x	x
SMM (380-480V, 18A, COL)	6SL3126-1TE21-8AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 18A, COL)	6SL3126-1TE21-8AA4	MOTOR MODULE	x	---	x	x
SMM (380-480V, 30A, COL)	6SL3126-1TE23-0AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 45A, COL)	6SL3126-1TE24-5AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 60A, COL)	6SL3126-1TE26-0AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 85A, COL)	6SL3126-1TE28-5AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 132A, COL)	6SL3126-1TE31-3AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 200A, COL)	6SL3126-1TE32-0AA3	MOTOR MODULE	x	---	x	---
SMM (380-480V, 200A, COL)	6SL3126-1TE32-0AA4	MOTOR MODULE	x	---	x	x
SMM (380-480V, 210A, INT, Chassis)	6SL3320-1TE32-1AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 210A, INT, Chassis)	6SL3320-1TE32-1AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 210A, INT, GG)	6SL3320-1TE32-1AC3	SPARE PART	x	---	x	x
SMM (380-480V, 260A, INT, Chassis)	6SL3320-1TE32-6AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 260A, INT, Chassis)	6SL3320-1TE32-6AA3	MOTOR MODULE	x	---	x	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The compliance of the designated product family modules with the requirements of the applied regulations and directives is indicated by "x".

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
SMM (380-480V, 260A, INT, GG)	6SL3320-1TE32-6AC3	SPARE PART	x	---	x	x
SMM (380-480V, 310A, INT, Chassis)	6SL3320-1TE33-1AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 310A, INT, Chassis)	6SL3320-1TE33-1AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 310A, INT, GG)	6SL3320-1TE33-1AC3	SPARE PART	x	---	x	x
SMM (380-480V, 380A, INT, Chassis)	6SL3320-1TE33-8AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 380A, INT, Chassis)	6SL3320-1TE33-8AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 380A, INT, GG)	6SL3320-1TE33-8AC3	SPARE PART	x	---	x	x
SMM (380-480V, 490A, INT, Chassis)	6SL3320-1TE35-0AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 490A, INT, Chassis)	6SL3320-1TE35-0AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 490A, INT, GG)	6SL3320-1TE35-0AC3	SPARE PART	x	---	x	x
SMM (380-480V, 605A, INT, EB)	6SL3320-1TE36-1AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 745A, INT, EB)	6SL3320-1TE37-5AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 840A, INT, EB)	6SL3320-1TE38-4AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 985A, INT, EB)	6SL3320-1TE41-0AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 1260A, INT, EB)	6SL3320-1TE41-2AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 1405A, INT, EB)	6SL3320-1TE41-4AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 1330A, INT, EB)	6SL3320-1TE41-4AS3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 85A, INT, Chassis)	6SL3320-1TG28-5AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 85A, INT, Chassis)	6SL3320-1TG28-5AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 85A, INT, GG)	6SL3320-1TG28-5AC3	SPARE PART	x	---	x	x
SMM (500-690V, 100A, INT, Chassis)	6SL3320-1TG31-0AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 100A, INT, Chassis)	6SL3320-1TG31-0AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 100A, INT, GG)	6SL3320-1TG31-0AC3	SPARE PART	x	---	x	x
SMM (500-690V, 120A, INT, Chassis)	6SL3320-1TG31-2AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 120A, INT, Chassis)	6SL3320-1TG31-2AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 120A, INT, GG)	6SL3320-1TG31-2AC3	SPARE PART	x	---	x	x
SMM (500-690V, 150A, INT, Chassis)	6SL3320-1TG31-5AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 150A, INT, Chassis)	6SL3320-1TG31-5AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 150A, INT, GG)	6SL3320-1TG31-5AC3	SPARE PART	x	---	x	x
SMM (500-690V, 175A, INT, Chassis)	6SL3320-1TG31-8AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 175A, INT, Chassis)	6SL3320-1TG31-8AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 175A, INT, GG)	6SL3320-1TG31-8AC3	SPARE PART	x	---	x	x
SMM (500-690V, 215A, INT, Chassis)	6SL3320-1TG32-2AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 215A, INT, Chassis)	6SL3320-1TG32-2AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 215A, INT, GG)	6SL3320-1TG32-2AC3	SPARE PART	x	---	x	x
SMM (500-690V, 260A, INT, Chassis)	6SL3320-1TG32-6AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 260A, INT, Chassis)	6SL3320-1TG32-6AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 260A, INT, GG)	6SL3320-1TG32-6AC3	SPARE PART	x	---	x	x
SMM (500-690V, 330A, INT, EB)	6SL3320-1TG33-3AA3	MOTOR MODULE	x	---	x	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The compliance of the designated product family modules with the requirements of the applied regulations and directives is indicated by "x".

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
SMM (500-690V, 330A, INT, GG)	6SL3320-1TG33-3AC3	SPARE PART	x	---	x	x
SMM (500-690V, 410A, INT, EB)	6SL3320-1TG34-1AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 465A, INT, EB)	6SL3320-1TG34-7AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 575A, INT, EB)	6SL3320-1TG35-8AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 735A, INT, EB)	6SL3320-1TG37-4AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 810A, INT, EB)	6SL3320-1TG38-1AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 910A, INT, EB)	6SL3320-1TG38-8AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 910A, INT, EB)	6SL3320-1TG38-8AA5	SPARE PART	x	---	x	x
SMM (500-690V, 1025A, INT, EB)	6SL3320-1TG41-0AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 1025A, INT, EB)	6SL3320-1TG41-0AA5	SPARE PART	x	---	x	x
SMM (500-690V, 1270A, INT, EB)	6SL3320-1TG41-3AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 1270A, INT, EB)	6SL3320-1TG41-3AA5	SPARE PART	x	---	x	x
SMM (500-690V, 1450A, INT, EB)	6SL3320-1TG41-5AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 85A, INT, Chassis)	6SL3320-1TH28-5AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 100A, INT, Chassis)	6SL3320-1TH31-0AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 120A, INT, Chassis)	6SL3320-1TH31-2AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 150A, INT, Chassis)	6SL3320-1TH31-5AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 175A, INT, Chassis)	6SL3320-1TH31-8AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 215A, INT, Chassis)	6SL3320-1TH32-2AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 260A, INT, Chassis)	6SL3320-1TH32-6AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 665A, INT, Chassis)	6SL3321-1TE36-6AA0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 740A, INT, Chassis)	6SL3321-1TE37-4AA0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 810A, INT, Chassis)	6SL3321-1TE38-1AA0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 910A, INT, Chassis)	6SL3321-1TE38-8AA0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 975A, INT, Chassis)	6SL3321-1TE41-0AA0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 1075A, INT, Chassis)	6SL3321-1TE41-1AA0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 1145A, INT, Chassis)	6SL3321-1TE41-2AA0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 1325A, INT, Chassis)	6SL3321-1TE41-3AA0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 1495A, INT, Chassis)	6SL3321-1TE41-5AA0	MOTOR MODULE	x	---	x	x
SMM (380-480V, 210A, LC, Chassis)	6SL3325-1TE32-1AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 210A, LC, Chassis)	6SL3325-1TE32-1AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 260A, LC, Chassis)	6SL3325-1TE32-6AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 260A, LC, Chassis)	6SL3325-1TE32-6AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 310A, LC, Chassis)	6SL3325-1TE33-1AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 310A, LC, Chassis)	6SL3325-1TE33-1AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 490A, LC, Chassis)	6SL3325-1TE35-0AA0	MOTOR MODULE	x	---	x	---
SMM (380-480V, 490A, LC, Chassis)	6SL3325-1TE35-0AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 605A, LC, EB)	6SL3325-1TE36-1AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 745A, LC, EB)	6SL3325-1TE37-5AA3	MOTOR MODULE	x	---	x	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The compliance of the designated product family modules with the requirements of the applied regulations and directives is indicated by "x".

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
SMM (380-480V, 745A, LC, EB)	6SL3325-1TE37-5AA7	MOTOR MODULE	x	---	x	x
SMM (380-480V, 840A, LC, EB)	6SL3325-1TE38-4AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 985A, LC, EB)	6SL3325-1TE41-0AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 985A, LC, EB)	6SL3325-1TE41-0AA7	MOTOR MODULE	x	---	x	x
SMM (380-480V, 1260A, LC, EB)	6SL3325-1TE41-2AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 1260A, LC, EB)	6SL3325-1TE41-2AA7	MOTOR MODULE	x	---	x	x
SMM (380-480V, 1405A, LC, EB)	6SL3325-1TE41-4AA3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 1405A, LC, EB)	6SL3325-1TE41-4AA7	MOTOR MODULE	x	---	x	x
SMM (380-480V, 1330A, LC, EB)	6SL3325-1TE41-4AS3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 100A, LC, Chassis)	6SL3325-1TG31-0AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 100A, LC, Chassis)	6SL3325-1TG31-0AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 150A, LC, Chassis)	6SL3325-1TG31-5AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 150A, LC, Chassis)	6SL3325-1TG31-5AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 215A, LC, Chassis)	6SL3325-1TG32-2AA0	MOTOR MODULE	x	---	x	---
SMM (500-690V, 215A, LC, Chassis)	6SL3325-1TG32-2AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 330A, LC, EB)	6SL3325-1TG33-3AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 465A, LC, EB)	6SL3325-1TG34-7AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 465A, LC, EB)	6SL3325-1TG34-7AA7	MOTOR MODULE	x	---	x	x
SMM (500-690V, 575A, LC, EB)	6SL3325-1TG35-8AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 575A, LC, EB)	6SL3325-1TG35-8AA7	MOTOR MODULE	x	---	x	x
SMM (500-690V, 735A, LC, EB)	6SL3325-1TG37-4AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 810A, LC, EB)	6SL3325-1TG38-0AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 810A, LC, EB)	6SL3325-1TG38-1AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 810A, LC, EB)	6SL3325-1TG38-1AA7	MOTOR MODULE	x	---	x	x
SMM (500-690V, 1025A, LC, EB)	6SL3325-1TG41-0AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 1025A, LC, EB)	6SL3325-1TG41-0AA7	MOTOR MODULE	x	---	x	x
SMM (500-690V, 1270A, LC, EB)	6SL3325-1TG41-3AA3	MOTOR MODULE	x	---	x	x
SMM (500-690V, 1270A, LC, EB)	6SL3325-1TG41-3AA7	MOTOR MODULE	x	---	x	x
SMM (500-690V, 1500A, LC, EB)	6SL3325-1TG41-6AA3	MOTOR MODULE	x	---	x	---
SMM (500-690V, 1500A, LC, EB)	6SL3325-1TG41-6AA7	MOTOR MODULE	x	---	x	x
SMM (500-690V, 1560A, LC, EB)	6SL3325-1TG41-6AP3	MOTOR MODULE	x	---	x	x
SMM (380-480V, 315-355kW, EB)	6SL3354-1TE37-4AA0	SPARE PART	x	---	x	x
SMM (380-480V, 400-450kW, EB)	6SL3354-1TE38-8AA0	SPARE PART	x	---	x	x
SMM (380-480V, 500-630kW, EB)	6SL3354-1TE41-2AA0	SPARE PART	x	---	x	x
SMM (380-480V, 710-800kW, EB)	6SL3354-1TE41-5AA0	SPARE PART	x	---	x	x
SMM (380-480V, 3A, INT, Compact)	6SL3420-1TE13-0AA1	MOTOR MODULE	x	---	x	x
SMM (380-480V, 5A, INT, Compact)	6SL3420-1TE15-0AA1	MOTOR MODULE	x	---	x	x
SMM (60V, 5A, INT, Compact)	6SL3420-1TE15-0AX1	MOTOR MODULE	x	---	x	x
SMM (380-480V, 9A, INT, Compact)	6SL3420-1TE21-0AA1	MOTOR MODULE	x	---	x	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The compliance of the designated product family modules with the requirements of the applied regulations and directives is indicated by "x".

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
SMM (380-480V, 18A, INT, Compact)	6SL3420-1TE21-8AA1	MOTOR MODULE	x	---	x	x
Double Motor Modules						
DMM (380-480V, 2x3A, INT)	6SL3120-2TE13-0AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x3A, INT)	6SL3120-2TE13-0AA3	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x3A, INT)	6SL3120-2TE13-0AA4	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x3A, INT)	6SL3120-2TE13-0AB0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x3A, INT)	6SL3120-2TE13-0AD0	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x3A, INT)	6SL3120-2TE13-0AD7	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x5A, INT)	6SL3120-2TE15-0AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x5A, INT)	6SL3120-2TE15-0AA3	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x5A, INT)	6SL3120-2TE15-0AA4	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x5A, INT)	6SL3120-2TE15-0AB0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x5A, INT)	6SL3120-2TE15-0AD0	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x5A, INT)	6SL3120-2TE15-0AD7	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x9A, INT)	6SL3120-2TE21-0AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x9A, INT)	6SL3120-2TE21-0AA3	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x9A, INT)	6SL3120-2TE21-0AA4	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x9A, INT)	6SL3120-2TE21-0AB0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x9A, INT)	6SL3120-2TE21-0AD0	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x9A, INT)	6SL3120-2TE21-0AD7	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x18A, INT)	6SL3120-2TE21-8AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x18A, INT)	6SL3120-2TE21-8AA3	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x18A, INT)	6SL3120-2TE21-8AB0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x18A, INT)	6SL3120-2TE21-8AC0	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x18A, INT)	6SL3120-2TE21-8AC7	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x18A, INT)	6SL3120-2TE21-8AD0	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x18A, INT)	6SL3120-2TE21-8AD7	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x3A, INT)	6SL3120-2TE13-0AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x5A, INT)	6SL3120-2VE15-0AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x9A, INT)	6SL3120-2VE21-0AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x3A, EXT)	6SL3121-2TE13-0AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x3A, EXT)	6SL3121-2TE13-0AA3	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x3A, EXT)	6SL3121-2TE13-0AA4	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x5A, EXT)	6SL3121-2TE15-0AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x5A, EXT)	6SL3121-2TE15-0AA3	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x5A, EXT)	6SL3121-2TE15-0AA4	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x9A, EXT)	6SL3121-2TE21-0AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x9A, EXT)	6SL3121-2TE21-0AA3	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x9A, EXT)	6SL3121-2TE21-0AA4	MOTOR MODULE	x	---	x	x

The compliance of the designated product family modules with the requirements of the applied regulations and directives is indicated by "x".

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
DMM (380-480V, 2x18A, EXT)	6SL3121-2TE21-8AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x18A, EXT)	6SL3121-2TE21-8AA3	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x3A, COL)	6SL3126-2TE13-0AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x3A, COL)	6SL3126-2TE13-0AA3	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x3A, COL)	6SL3126-2TE13-0AA4	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x5A, COL)	6SL3126-2TE15-0AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x5A, COL)	6SL3126-2TE15-0AA3	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x5A, COL)	6SL3126-2TE15-0AA4	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x9A, COL)	6SL3126-2TE21-0AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x9A, COL)	6SL3126-2TE21-0AA3	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x9A, COL)	6SL3126-2TE21-0AA4	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x18A, COL)	6SL3126-2TE21-8AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x18A, COL)	6SL3126-2TE21-8AA3	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x1.7A, INT, Compact)	6SL3420-2TE11-7AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x1.7A, INT, Compact)	6SL3420-2TE11-7AA1	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x3A, INT, Compact)	6SL3420-2TE13-0AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x3A, INT, Compact)	6SL3420-2TE13-0AA1	MOTOR MODULE	x	---	x	x
DMM (380-480V, 2x5A, INT, Compact)	6SL3420-2TE15-0AA0	MOTOR MODULE	x	---	x	---
DMM (380-480V, 2x5A, INT, Compact)	6SL3420-2TE15-0AA1	MOTOR MODULE	x	---	x	x
Combi Motor Modules						
COMBI (380-480V, 16kW, 24A-9A-9A, EXT)	6SL3111-3VE21-6EA0	MOTOR MODULE	x	---	x	---
COMBI (380-480V, 16kW, 24A-9A-9A, EXT)	6SL3111-3VE21-6EA1	MOTOR MODULE	x	---	x	x
COMBI (380-480V, 16kW, 18A-5A-5A, EXT)	6SL3111-3VE21-6FA0	MOTOR MODULE	x	---	x	---
COMBI (380-480V, 16kW, 18A-5A-5A, EXT)	6SL3111-3VE21-6FA1	MOTOR MODULE	x	---	x	x
COMBI (380-480V, 16kW, 18A-5A-5A, EXT)	6SL3111-3VE21-6FA2	MOTOR MODULE	x	---	x	x
COMBI (380-480V, 20kW, 30A-9A-9A, EXT)	6SL3111-3VE22-0HA0	MOTOR MODULE	x	---	x	---
COMBI (380-480V, 20kW, 30A-9A-9A, EXT)	6SL3111-3VE22-0HA1	MOTOR MODULE	x	---	x	x
COMBI (380-480V, 10kW, 24A-12A-12A-12A, EXT)	6SL3111-4VE21-0EA0	MOTOR MODULE	x	---	x	---
COMBI (380-480V, 10kW, 24A-12A-12A-12A, EXT)	6SL3111-4VE21-0EA1	MOTOR MODULE	x	---	x	x
COMBI (380-480V, 16kW, 24A-9A-9A-9A, EXT)	6SL3111-4VE21-6EA0	MOTOR MODULE	x	---	x	---
COMBI (380-480V, 16kW, 24A-9A-9A-9A, EXT)	6SL3111-4VE21-6EA1	MOTOR MODULE	x	---	x	x
COMBI (380-480V, 16kW, 24A-12A-9A-9A, EXT)	6SL3111-4VE21-6EC1	MOTOR MODULE	x	---	x	x
COMBI (380-480V, 16kW, 24A-12A-9A-9A, EXT)	6SL3111-4VE21-6ED1	MOTOR MODULE	x	---	x	x
COMBI (380-480V, 16kW, 18A-9A-5A-5A, EXT)	6SL3111-4VE21-6FA0	MOTOR MODULE	x	---	x	---
COMBI (380-480V, 16kW, 18A-9A-5A-5A, EXT)	6SL3111-4VE21-6FA1	MOTOR MODULE	x	---	x	x
COMBI (380-480V, 16kW, 18A-9A-5A-5A, EXT)	6SL3111-4VE21-6FA2	MOTOR MODULE	x	---	x	x
COMBI (380-480V, 20kW, 30A-12A-9A-9A, EXT)	6SL3111-4VE22-0HA0	MOTOR MODULE	x	---	x	---
COMBI (380-480V, 20kW, 30A-12A-9A-9A, EXT)	6SL3111-4VE22-0HA1	MOTOR MODULE	x	---	x	x
HF-Spindle						

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The compliance of the designated product family modules with the requirements of the applied regulations and directives is indicated by "x".

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
HF MOTOR MODULE 225A, 16KHZ	6SL3125-1UE32-2AA0	MOTOR MODULE	x	---	x	x
HF DRIVE 225A, 16KHZ	6SL3125-1UE32-2AD0	DRIVE	x	---	x	x
HF CHOKE MODULE 225A, 16KHZ	6SL3125-2UE32-2AA0	FILTER	---	x	x	x
HF DAMPING MODULE 225A, 16KHZ	6SL3125-3UE32-2AA0	DAMPING	---	x	x	x
Motor Integrated Modules						
S120M (500-690V, AH36)	6SL3532-6DF71-0RA1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH36)	6SL3532-6DF71-0RA2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH36)	6SL3532-6DF71-0RB1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH36)	6SL3532-6DF71-0RB2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH36)	6SL3532-6DF71-0RG1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH36)	6SL3532-6DF71-0RG2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH36)	6SL3532-6DF71-0RH1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH36)	6SL3532-6DF71-0RH2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3540-6DF71-0RA1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3540-6DF71-0RA2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3540-6DF71-0RB1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3540-6DF71-0RB2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3540-6DF71-0RG1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3540-6DF71-0RG2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3540-6DF71-0RH1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3540-6DF71-0RH2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3542-6DF71-0RA1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3542-6DF71-0RA2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3542-6DF71-0RB1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3542-6DF71-0RB2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3542-6DF71-0RG1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3542-6DF71-0RG2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3542-6DF71-0RH1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH48)	6SL3542-6DF71-0RH2	MOTOR MODULE	x	---	x	x
S120M DRIVE-CLiQ Extension	6SL3555-0AA00-6AB0	ADAPTER KIT	---	x	---	x
S120M AM600	6SL3555-2BC10-0AA0	ADAPTER MODULE	x	---	x	x
S120M Hybrid Cabinet Bushing (HCB)	6SL3555-2DA00-0AA0	CABINET BUSHING	---	x	---	x
S120M (500-690V, AH63)	6SL3562-6DF71-0RA1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3562-6DF71-0RA2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3562-6DF71-0RB1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3562-6DF71-0RB2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3562-6DF71-0RG1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3562-6DF71-0RG2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3562-6DF71-0RH1	MOTOR MODULE	x	---	x	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The compliance of the designated product family modules with the requirements of the applied regulations and directives is indicated by "x".

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
S120M (500-690V, AH63)	6SL3562-6DF71-0RH2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3563-6DC71-0RA1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3563-6DC71-0RB1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3563-6DF71-0RA1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3563-6DF71-0RA2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3563-6DF71-0RB1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3563-6DF71-0RB2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3563-6DF71-0RG1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3563-6DF71-0RG2	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3563-6DF71-0RH1	MOTOR MODULE	x	---	x	x
S120M (500-690V, AH63)	6SL3563-6DF71-0RH2	MOTOR MODULE	x	---	x	x
Power Modules						
PM (380-480V, 210A, INT, Chassis)	6SL3310-1TE32-1AA0	POWER MODULE	x	---	x	---
PM (380-480V, 210A, INT, Chassis)	6SL3310-1TE32-1AA3	POWER MODULE	x	---	x	x
PM (380-480V, 260A, INT, Chassis)	6SL3310-1TE32-6AA0	POWER MODULE	x	---	x	---
PM (380-480V, 260A, INT, Chassis)	6SL3310-1TE32-6AA3	POWER MODULE	x	---	x	x
PM (380-480V, 310A, INT, Chassis)	6SL3310-1TE33-1AA0	POWER MODULE	x	---	x	---
PM (380-480V, 310A, INT, Chassis)	6SL3310-1TE33-1AA3	POWER MODULE	x	---	x	x
PM (380-480V, 380A, INT, Chassis)	6SL3310-1TE33-8AA0	POWER MODULE	x	---	x	---
PM (380-480V, 380A, INT, Chassis)	6SL3310-1TE33-8AA3	POWER MODULE	x	---	x	x
PM (380-480V, 490A, INT, Chassis)	6SL3310-1TE35-0AA0	POWER MODULE	x	---	x	---
PM (380-480V, 490A, INT, Chassis)	6SL3310-1TE35-0AA3	POWER MODULE	x	---	x	x
PM (380-480V, 210A, LC, Chassis)	6SL3315-1TE32-1AA0	POWER MODULE	x	---	x	---
PM (380-480V, 210A, LC, Chassis)	6SL3315-1TE32-1AA3	POWER MODULE	x	---	x	x
PM (380-480V, 260A, LC, Chassis)	6SL3315-1TE32-6AA0	POWER MODULE	x	---	x	---
PM (380-480V, 260A, LC, Chassis)	6SL3315-1TE32-6AA3	POWER MODULE	x	---	x	x
PM (380-480V, 310A, LC, Chassis)	6SL3315-1TE33-1AA0	POWER MODULE	x	---	x	---
PM (380-480V, 310A, LC, Chassis)	6SL3315-1TE33-1AA3	POWER MODULE	x	---	x	x
PM (380-480V, 490A, LC, Chassis)	6SL3315-1TE35-0AA0	POWER MODULE	x	---	x	---
PM (380-480V, 490A, LC, Chassis)	6SL3315-1TE35-0AA3	POWER MODULE	x	---	x	x
PM (380-480V, 315kW, LC, Chassis)	6SL3315-1TE36-1AA7	POWER MODULE	x	---	x	x
PM (380-480V, 400kW, LC, Chassis)	6SL3315-1TE37-5AA7	POWER MODULE	x	---	x	x
PM (500-690V, 400kW, LC, Chassis)	6SL3315-1TG34-1AA7	POWER MODULE	x	---	x	x
PM (500-690V, 450kW, LC, Chassis)	6SL3315-1TG34-7AA7	POWER MODULE	x	---	x	x
PM (500-690V, 560kW, LC, Chassis)	6SL3315-1TG35-8AA7	POWER MODULE	x	---	x	x