

OPTIMAL FOR THE PC-BASED AUTOMATION











SIMATIC IPC powered by SITOP

As digitalization grows, the demands on computing power, functionality and availability of industrial PCs are increasing. SIMATIC IPC offers a wide range of innovative product series that will meet your needs for years to come. A reliable power supply is a prerequisite for stable operation. SITOP offers the

right power supply for all SIMATIC IPCs with 24 V DC input, even when NEC Class 2 supply is required. For buffering in the event of a power failure and for safe shutdown of the PC, the SITOP power supply units can be upgraded to an uninterruptible DC power supply (DC UPS). The UPS modules can communi-





cate with the PC via USB or Industrial Ethernet/PROFINET and can be easily configured and diagnosed using the SITOP Manager in Windows. This brochure offers recommendations for the matching power supply and DC UPS for the SIMATIC IPC product series without additional loads.

SIMATIC IPCs with DC input






	SIMATIC High-end IPC	Embedded industrial PCs fanless			SIMATIC Basic IPC	Flat Panel
Box	IPC627E 	IPC127E 	IPC227G 	IPC427E 	IPC327G 	IFP Basic 
Panel	IPC677E 		IPC277G 	IPC477E 	IPC377G 	
	High performance	Ultra-compact	Compact	Powerful	Available ex stock	Robust monitors



The right power supply for every application

Advanced	Standard	Basic	DC/DC converter
 SITOP PSU8600 SITOP PSU8200 NEC Class 2	 SITOP PSU6200 SITOP smart NEC Class 2	 SITOP lite LOGO!Power NEC Class 2	 SITOP PSU3400 SITOP PSU400M NEC Class 2

... individually extendable with add-on modules to all-round protection

Redundancy modules  NEC Class 2 Failure of a power supply	Selectivity modules  NEC Class 2 Overload in 24 V load circuit	Buffer module  Power failure on the input side Seconds	DC UPS with ... capacitors  DC UPS with ... batteries  Hours
---	--	---	---



24 V DC Power supply

SIMATIC IPC (24 V DC)	Min. input voltage [V]	Max. inrush current [A]	Rated current [A]	Recommended power supply w/o DC UPS		Recommended power supply with DC UPS	
				Power supply 24 V DC	Article no.	Power supply 24 V DC	Article no.
IPC127E	19.2	1.8	0.7	LOGO!Power 1.3 A SITOP PSU6200 1.3 A	6EP3331-6SB00-0AY0 6EP3331-7SB00-0AX0	SITOP PSU6200 5 A	6EP3333-7SB00-0AX0
IPC227G	19.2	1.9	1.9	LOGO!Power 2.5 A SITOP PSU6200 2.5 A	6EP3333-7LB00-0AX0 6EP3332-6SB00-0AX0	SITOP PSU6200 5 A	6EP3333-7SB00-0AX0
IPC277G (7", 10")	19.2	1.9	1.9			SITOP PSU6200 5 A	6EP3333-7SB00-0AX0
IPC277G (12", 15", 19", 22", 24")	19.2	5	5	SITOP PSU6200 5 A	6EP3333-7SB00-0AX0	SITOP PSU6200 10 A	6EP3334-7SB00-3AX0
IPC327G	19.2	2.5	2.5				
IPC377G (12", 15", 19", 22")	19.2	2.5	2.5	LOGO!Power 2.5 A SITOP PSU6200 2.5 A	6EP3333-7LB00-0AX0 6EP3332-6SB00-0AX0	SITOP PSU6200 5 A	6EP3333-7SB00-0AX0
IPC427E	19.2	6.5	3.4	SITOP PSU6200 3.7 A	6EP3333-7LB00-0AX0	SITOP PSU6200 10 A	6EP3334-7SB00-3AX0
IPC477E	19.2	6.5	3.4	SITOP PSU6200 5 A	6EP3333-7SB00-0AX0	SITOP PSU6200 10 A	6EP3334-7SB00-3AX0
IPC627E	19.2	13	8				
IPC627E (5 slot)	19.2	13	8	SITOP PSU6200 10 A	6EP3334-7SB00-3AX0	SITOP PSU6200 20 A	6EP3336-7SB00-3AX0
IPC677E	19.2	14	8				
IOT2050	12	1.7	0.5	LOGO!Power 2.5 A SITOP PSU6200 2.5 A	6EP3332-6SB00-0AY0 6EP3332-6SB00-0AX0	SITOP PSU6200 5 A	6EP3333-7SB00-0AX0
IFP basic	20.4	2.5	2.5				

24 V DC supply according to NEC Class 2 (max. 100 W)

24 V DC power supply, NEC Class 2 not necessary

Add-on module with NEC Class 2 necessary
➤ see configuration examples on the next page



DC UPS

For brief voltage drops
(bridging min. 15 seconds):
SITOP UPS500S

SITOP UPS500S:
Appr. 8 years service life¹⁾
at 20°C ambient
temperature

For bridging longer power failures:
SITOP UPS1600 (DC UPS module) + SITOP UPS1100 (battery module)

SITOP UPS1600:
In combination with
battery module UPS1100
lead or lithium

BAT1600 lead battery:
Appr. 4 years service
life¹⁾ at 20°C ambient
temperature

BAT1600 lithium battery
(LiFePO4):
Appr. 11 years service
life¹⁾ at 20°C ambient
temperature

SIMATIC IPC	Rated current [A]	Recommended UPS: Maintenance-free DC UPS in capacitor technology, with USB interface	Recommended UPS modules:		
			– 0AY0: Signaling contacts – 1AY0: USB interface – 2AY0: Ethernet/PROFINET	Recommended lead battery. Bridging time min. 15 min.	Recommended LiFePO4 battery (Lithium-Ferrite- Phosphate). Bridging time min. 20 min.
IPC127E	1.8	6EP1933-2EC41	6EP4134-3AB00-□AY0	6EP4133-0GA00-0AY0	6EP4132-0JA00-0AY0
IPC227E	1.8	2.5 kW	10 A	3.2 Ah	2.5 Ah
IPC277E (7", 9")	1.4				
IPC277E (12", 15", 19")	3				
IPC327E	2.5				
IPC377E (12", 15", 19")	2.5				
IPC427E	3.4				
IPC477E	3.4				
IPC627E	8	6EP1933-2EC51	6EP4136-3AB00-□AY0		
IPC627E (5 slot)	8	5 kW			6EP4134-0JA00-0AY0
IPC677E	8		20 A		7.5 Ah
IOT2040	0.5	6EP1933-2EC41	6EP4134-3AB00-□AY0		6EP4132-0JA00-0AY0
IFP Basic	2.5	2.5 kW	10 A		2.5 Ah

¹⁾ Drop to 80% of the original capacity, depending on battery temperature
Specifications at rated input voltage and ambient temperature +25°C (unless otherwise specified)



Uninterruptible 24 V DC supply in NEC Class 2 for SIMATIC IPC


If SIMATIC IPCs with the required NEC Class 2 supply (max. 100 VA) are supplied via a DC UPS, it is not enough to use a power supply with NEC Class 2. This is because in buffer mode the IPC is supplied via the energy storage device (battery or capacitors), which does not limit the power output. SITOP add-on modules in NEC Class 2

ensure that the power limitation to 100 VA is maintained in both mains and buffer operation. This allows for the use of a more powerful power supply unit. Only the IPC according to NEC Class 2 is supplied by the redundancy module PSE202U 3.5 A. The PSE200U 4 x 3 A selectivity module is your best choice when several loads


are supplied while also being protected against overload.

With the CNX8600 8 x 2.5 A module, the SITOP PSU8600 power supply system also offers selective protection for NEC Class 2 outputs, which are protected against power failure by the system's own UPS modules.


SIMATIC IPC supply with a powerful power supply unit and capacitor based DC UPS SITOP UPS500S and redundancy module SITOP PSE202U 3.5 A NEC Class 2



SIMATIC IPC supply with a powerful power supply unit and DC UPS module SITOP UPS1600 with battery module UPS1100 and selectivity module SITOP PSE200U 4 x 3 A NEC Class 2



SIMATIC IPC supply via power supply system SITOP PSU8600 with expansion module CNX8600 NEC Class 2 and buffering of outputs via DC UPS module SITOP UPS8600 with battery module SITOP BAT8600



Find out more:
[siemens.com/ipc](https://www.siemens.com/ipc)
[siemens.com/sitop](https://www.siemens.com/sitop)
TIA Selection Tool:
[siemens.com/tst](https://www.siemens.com/tst)

Subject to changes and errors. The information provided in this brochure contains descriptions or performance characteristics which, in case of actual use, do not always apply as described or which may change as a result of further development of the products. The desired performance characteristics are only binding if expressly agreed in the contract. Availability and technical specifications are subject to change without notice.

All product designations may be trademarks or product names of Siemens AG or supplier companies, the use of which by third parties for their own purposes may violate the rights of the owners.

Industrial Security

Siemens provides automation and drive products with industrial-security functions that support the secure operation of plants or machines. They are an important component in a holistic industrial-security concept. With this in mind, our products undergo continuous development. We therefore recommend that you keep yourself informed with respect to our product updates and that you use only the latest versions. Please find further information on this subject at **[automation.siemens.com/support](https://www.automation.siemens.com/support)**.

You may also register for a product-specific newsletter at this address.

To ensure the secure operation of a plant or machine it is also necessary to take suitable preventive action (e.g., cell protection concept) and to integrate the automation and drive components into a state-of-the-art holistic industrial-security concept for the entire plant or machine. Any third-party products that may be in use must also be taken into account. Please find further information at **[siemens.com/industrialsecurity](https://www.siemens.com/industrialsecurity)**.

Published by Siemens AG

Digital Industries
Process Automation
Östliche Rheinbrückenstr. 50
76187 Karlsruhe, Germany

For the U.S. published by Siemens Industry Inc

100 Technology Drive
Alpharetta, GA 30005
United States

Article No.: DIPA-B10309-00-7600
Dispo 26000
WS 04220.0
Printed in Germany
© Siemens 2022