

Interface modules with CPU		
PLC on base S7-300		Article number
IM154-8 PN/DP CPU 384KB		6ES7154-8AB01-0AB0
IM154-8F PN/DP CPU 512KB		6ES7154-8FB01-0AB0
IM154-8FX PN/DP CPU 1,5MB		6ES7154-8FX00-0AB0
Connection module		Article number
CM IM PN DP M12, 7/8"		6ES7194-4AN00-0AA0
Interfaces		Article number
X01 DP1 (M12 pin)		
non-assembled connectors		
PROFIBUS M12 connector 180° w ith socket insert		6GK1905-0EB00
PROFIBUS M12 connector fast connect 180° w ith socket insert		6GK1905-0EB10
non-assembled cables		
PROFIBUS FC cable		
- FC Standard Cable		6XV1830-0EH10
- FC Trailing Cable		6XV1830-3EH10
- FC Food Cable (PE sheath)		6XV1830-0GH10
- FC Robust Cable (PUR sheath)		6XV1830-0JH10
- FC FRNC Cable (FRNC sheath)		6XV1830-0LH10
- FC Underground Cable		6XV1830-3FH10
- Festoon Cable GP (PVC sheath)		6XV1830-3GH10
- FC Flexible Cable GP (PUR sheath)		6XV1831-2K

pre-assembled cables		
PROFIBUS M12 connecting cable, trailable, pre-assembled at both ends with PROFIBUS M12 connectors 180° (one end socket, one end pin)	0,3m	6XV1830-3DE30
	0,5m	6XV1830-3DE50
	1,0m	6XV1830-3DH10
	1,5 m	6XV1830-3DH15
	2,0 m	6XV1830-3DH20
	3,0 m	6XV1830-3DH30
	5,0 m	6XV1830-3DH50
	10,0 m	6XV1830-3DN10
PROFIBUS M12 connecting cable, trailable, pre-assembled at both ends with PROFIBUS M12 connectors angled (one end socket, one end pin)	15,0 m	6XV1830-3DN15
	1,5 m	6XV1830-3DH15-OSB0 ¹⁾
	2,0 m	6XV1830-3DH20-OSB0 ¹⁾
	3,0 m	6XV1830-3DH30-OSB0 ¹⁾
	5,0 m	6XV1830-3DH50-OSB0 ¹⁾
	10,0 m	6XV1830-3DN10-OSB0 ¹⁾
15,0 m	6XV1830-3DN15-OSB0 ¹⁾	
M12 bus termination connector PROFIBUS, socket insert		6GK1905-0ED00
M12 cover caps		6ES7194-4JD60-0AA0
M12 cover caps		3RK1901-1KA00
X01 DP2 (M12-socket)		
non-assembled connectors		
PROFIBUS M12 connector 180° with plug insert		6GK1905-0EA00
PROFIBUS M12 connector fast connect 180° with plug insert		6GK1905-0EA10
non-assembled cables		
PROFIBUS FC cable		
- FC Standard Cable		6XV1830-0EH10
- FC Trailing Cable		6XV1830-3EH10
- FC Food Cable (PE sheath)		6XV1830-0GH10
- FC Robust Cable (PUR sheath)		6XV1830-0JH10
- FC FRNC Cable (FRNC sheath)		6XV1830-0LH10
- FC Underground Cable		6XV1830-3FH10
- Festoon Cable GP (PVC sheath)		6XV1830-3GH10
- FC Flexible Cable GP (PUR sheath)		6XV1831-2K

pre-assembled cables		
PROFIBUS M12 connecting cable, trailable, pre-assembled at both ends with PROFIBUS M12 connectors 180° (one end socket, one end pin)	0,3m	6XV1830-3DE30
	0,5m	6XV1830-3DE50
	1,0m	6XV1830-3DH10
	1,5 m	6XV1830-3DH15
	2,0 m	6XV1830-3DH20
	3,0 m	6XV1830-3DH30
	5,0 m	6XV1830-3DH50
	10,0 m	6XV1830-3DN10
	15,0 m	6XV1830-3DN15
PROFIBUS M12 connecting cable, trailable, pre-assembled at both ends with PROFIBUS M12 connectors angled (one end socket, one end pin)	1,5 m	6XV1830-3DH15-0SB0 ¹⁾
	2,0 m	6XV1830-3DH20-0SB0 ¹⁾
	3,0 m	6XV1830-3DH30-0SB0 ¹⁾
	5,0 m	6XV1830-3DH50-0SB0 ¹⁾
	10,0 m	6XV1830-3DN10-0SB0 ¹⁾
	15,0 m	6XV1830-3DN15-0SB0 ¹⁾
M12 bus termination connector PROFIBUS, male insert		6GK1905-0EC00
M12 cover caps		3RX9802-0AA00
M12 cover caps		3RK1901-1KA00
X02 P1 (M12 socket)		
non-assembled connectors		
PROFINET M12 connector, d-coded with FastConnect system, 180°		
- 1 per pack		6GK1901-0DB20-6AA0
- 8 per pack		6GK1901-0DB20-6AA8
PROFINET M12 connector, d-coded with FastConnect system, 180°		
- 1 per pack		6GK1901-0DB10-6AA0
- 8 per pack		6GK1901-0DB10-6AA8
PROFINET M12 connector, d-coded, angled		3RK1902-2DA00
non-assembled cables		
PROFINET FC cable		
- FC TP Standard Cable		6XV1840-2AH10
- FC TP Trailing Cable		6XV1840-3AH10

- FC TP Trailing Cable GP		6XV1870-2D
- FC TP Marine Cable		6XV1840-4AH10
- FC TP Torsion Cable		6XV1870-2F
- FC TP Flexible Cable GP		6XV1870-2B
- FC TP FRNC Cable		6XV1871-2F
- FC TP Food Cable		6XV1871-2L
- FC TP Festoon Cable GP		6XV1871-2S
pre-assembled cables		
PROFINET M12 trailable connecting cable, pre-assembled at both ends with M12 connectors 180° (plug)	0,3 m	6XV1870-8AE30
	0,5 m	6XV1870-8AE50
	1,0 m	6XV1870-8AH10
	1,5 m	6XV1870-8AH15
	2,0 m	6XV1870-8AH20
	3,0 m	6XV1870-8AH30
	5,0 m	6XV1870-8AH50
	10,0 m	6XV1870-8AN10
PROFINET M12 trailable connecting cable, pre-assembled at both ends with M12 connectors angled (plug)	0,3 m	6XV1870-8GE30
	0,5 m	6XV1870-8GE50
	1,0 m	6XV1870-8GH10
	1,5 m	6XV1870-8GH15
	2,0 m	6XV1870-8GH20
	3,0 m	6XV1870-8GH30
	5,0 m	6XV1870-8GH50
	10,0 m	6XV1870-8GN10
PROFINET M12 trailable connecting cable, pre-assembled at one end with M12 connector, angled (one end plug, one end open cable)	3,0 m	3RK1902-2HB30
	5,0 m	3RK1902-2HB50
	10,0 m	3RK1902-2HC10
PROFINET M12 trailable connecting cable, pre-assembled at one end with M12 connector 180° (one end plug, one end with RJ45 Plug 145°)	2,0 m	6XV1871-5TH20
	3,0 m	6XV1871-5TH30
	5,0 m	6XV1871-5TH50
	10,0 m	6XV1871-5TN10
	15,0 m	6XV1871-5TN15
M12 cover caps		3RX9802-0AA00
M12 cover caps		3RK1901-1KA00

X02 P2 (M12 socket)		
non-assembled connectors		
PROFINET M12 connector, d-coded with FastConnect system, 180°		
- 1 per pack		6GK1901-0DB20-6AA0
- 8 per pack		6GK1901-0DB20-6AA8
PROFINET M12 connector, d-coded with FastConnect system, 180°		
- 1 per pack		6GK1901-0DB10-6AA0
- 8 per pack		6GK1901-0DB10-6AA8
PROFINET M12 connector, d-coded, angled		3RK1902-2DA00
non-assembled cables		
PROFINET FC cable		
- FC TP Standard Cable		6XV1840-2AH10
- FC TP Trailing Cable		6XV1840-3AH10
- FC TP Trailing Cable GP		6XV1870-2D
- FC TP Marine Cable		6XV1840-4AH10
- FC TP Torsion Cable		6XV1870-2F
- FC TP Flexible Cable GP		6XV1870-2B
- FC TP FRNC Cable		6XV1871-2F
- FC TP Food Cable		6XV1871-2L
- FC TP Festoon Cable GP		6XV1871-2S
pre-assembled cables		
PROFINET M12 trailable connecting cable, pre-assembled at both ends with M12 connectors 180° (plug)	0,3 m	6XV1870-8AE30
	0,5 m	6XV1870-8AE50
	1,0 m	6XV1870-8AH10
	1,5 m	6XV1870-8AH15
	2,0 m	6XV1870-8AH20
	3,0 m	6XV1870-8AH30
	5,0 m	6XV1870-8AH50
	10,0 m	6XV1870-8AN10
	15,0 m	6XV1870-8AN15
PROFINET M12 trailable connecting cable, pre-assembled at both ends with M12 connectors angled (plug)	0,3 m	6XV1870-8GE30
	0,5 m	6XV1870-8GE50

	1,0 m	6XV1870-8GH10
	1,5 m	6XV1870-8GH15
	2,0 m	6XV1870-8GH20
	3,0 m	6XV1870-8GH30
	5,0 m	6XV1870-8GH50
	10,0 m	6XV1870-8GN10
	15,0 m	6XV1870-8GN15
PROFINET M12 trailable connecting cable, pre-assembled at one end with M12 connector, angled (one end plug, one end open cable)	3,0 m	3RK1902-2HB30
	5,0 m	3RK1902-2HB50
	10,0 m	3RK1902-2HC10
PROFINET M12 trailable connecting cable, pre-assembled at one end with M12 connector 180° (one end plug, one end with RJ45 Plug 145°)	2,0 m	6XV1871-5TH20
	3,0 m	6XV1871-5TH30
	5,0 m	6XV1871-5TH50
	10,0 m	6XV1871-5TN10
	15,0 m	6XV1871-5TN15
M12 cover caps		3RX9802-0AA00
M12 cover caps		3RK1901-1KA00
X03 DC 24V 7/8" (pin)		
non-assembled connectors		
7/8" connector 180° with socket insert		6GK1905-0FB00
7/8" connector angled with socket insert		3RK1902-3DA00
non-assembled cables		
Energy Cable, trailable, 5 x 1,5 mm ²		6XV1830-8AH10
pre-assembled cables		
7/8" connecting cable for supplying trailable energy cable, 5 x 1,5 mm ² , pre-assembled at both ends with 7/8" connectors 180° (one end socket, one end pin)	0,3m	6XV1822-5BE30
	0,5m	6XV1822-5BE50
	1,0m	6XV1822-5BH10
	1,5 m	6XV1822-5BH15
	2,0 m	6XV1822-5BH20
	3,0 m	6XV1822-5BH30
	5,0 m	6XV1822-5BH50
	10,0 m	6XV1822-5BN10
	15,0 m	6XV1822-5BN15
7/8" connecting cable for supplying trailable energy cable, 5 x 1,5 mm ² , pre-assembled at both ends with 7/8" connectors angled (one end socket, one end pin)	1,5 m	6XV1822-5BH15-0SB0 ¹⁾
	2,0 m	6XV1822-5BH20-0SB0 ¹⁾
	3,0 m	3RK1902-3NB30
	5,0 m	3RK1902-3NB50
	10,0 m	3RK1902-3NC10
	15,0 m	6XV1822-5BN15-0SB0 ¹⁾

7/8" connecting cable for supplying trailable energy cable, 5 x 1,5 mm ² , pre assembled at one end with 7/8" connector angled (one end socket, one end open cable)	3,0 m	3RK1902-3GB30
	5,0 m	3RK1902-3GB50
	10,0 m	3RK1902-3GC10
X04 DC 24V 7/8" (socket)		
non-assembled connectors		
7/8" connector 180° with pin insert		6GK1905-0FA00
7/8" connector angled with pin insert		3RK1902-3BA00
non-assembled cables		
Energy Cable, trailable, 5 x 1,5 mm ²		6XV1830-8AH10
pre-assembled cables		
7/8" connecting cable vor supplying trailable energy cable, 5 x 1,5 mm ² , pre-assembled at both ends with 7/8" connectors 180° (one end socket, one end pin)	0,3m	6XV1822-5BE30
	0,5m	6XV1822-5BE50
	1,0m	6XV1822-5BH10
	1,5 m	6XV1822-5BH15
	2,0 m	6XV1822-5BH20
	3,0 m	6XV1822-5BH30
	5,0 m	6XV1822-5BH50
	10,0 m	6XV1822-5BN10
	15,0 m	6XV1822-5BN15
7/8" connecting cable vor supplying trailable energy cable, 5 x 1,5 mm ² , pre-assembled at both ends with 7/8" connectors angled (one end socket, one end pin)	1,5 m	6XV1822-5BH15-OSB0 ¹⁾
	2,0 m	6XV1822-5BH20-OSB0 ¹⁾
	3,0 m	3RK1902-3NB30
	5,0 m	3RK1902-3NB50
	10,0 m	3RK1902-3NC10
15,0 m	6XV1822-5BN15-OSB0 ¹⁾	
7/8" cover caps		6ES7194-3JA00-0AA0
X2 P3 (RJ45)		
non-assembled connectors		
PROFINET RJ45 connector with FastConnect system, 180°		
- 1 per pack		6GK1901-1BB10-2AA0
- 10 per pack		6GK1901-1BB10-2AB0
PROFINET RJ45 connector with FastConnect system, angled		
- 1 per pack		6GK1901-1BB20-2AA0
- 10 per pack		6GK1901-1BB20-2AB0

pre-assembled cables		
Twisted-pair connecting cable 4x2 with RJ45 connector	0,5 m	6XV1870-3QE50
	1,0 m	6XV1870-3QH10
	2,0 m	6XV1870-3QH20
	6,0 m	6XV1870-3QH60
	10,0 m	6XV1870-3QN10
Crossed twisted-pair connecting cable 4x2 with RJ45 connectors	0,5 m	6XV1870-3RE50
	1,0 m	6XV1870-3RH10
	2,0 m	6XV1870-3RH20
	6,0 m	6XV1870-3RH60
	10,0 m	6XV1870-3RN10

¹⁾ Ordering with ORG-ID: 10001539

PLC on base S7-300		Article number
CPU 1516pro-2 PN		6ES7516-2PN00-0AB0
CPU 1516pro F-2 PN		6ES7516-2GN00-0AB0
Connection module		Article number
CM CPU 2PN M12, 7/8"		6ES7194-4AP00-0AA0
Interfaces		Article number
X1 P1 R (M12 pin)		
non-assembled connectors		
PROFINET M12 connector, d-coded with FastConnect system, 180°		
- 1 per pack		6GK1901-0DB20-6AA0
- 8 per pack		6GK1901-0DB20-6AA8
PROFINET M12 connector, d-coded with FastConnect system, 180°		
- 1 per pack		6GK1901-0DB10-6AA0
- 8 per pack		6GK1901-0DB10-6AA8
PROFINET M12 connector, d-coded, angled		3RK1902-2DA00
non-assembled cables		
PROFINET FC cable		
- FC TP Standard Cable		6XV1840-2AH10
- FC TP Trailing Cable		6XV1840-3AH10
- FC TP Trailing Cable GP		6XV1870-2D

- FC TP Marine Cable		6XV1840-4AH10
- FC TP Torsion Cable		6XV1870-2F
- FC TP Flexible Cable GP		6XV1870-2B
- FC TP FRNC Cable		6XV1871-2F
- FC TP Food Cable		6XV1871-2L
- FC TP Festoon Cable GP		6XV1871-2S
pre-assembled cables		
PROFINET M12 trailable connecting cable, pre-assembled at both ends with M12 connectors 180° (plug)	0,3 m	6XV1870-8AE30
	0,5 m	6XV1870-8AE50
	1,0 m	6XV1870-8AH10
	1,5 m	6XV1870-8AH15
	2,0 m	6XV1870-8AH20
	3,0 m	6XV1870-8AH30
	5,0 m	6XV1870-8AH50
	10,0 m	6XV1870-8AN10
PROFINET M12 trailable connecting cable, pre-assembled at both ends with M12 connectors angled (plug)	0,3 m	6XV1870-8GE30
	0,5 m	6XV1870-8GE50
	1,0 m	6XV1870-8GH10
	1,5 m	6XV1870-8GH15
	2,0 m	6XV1870-8GH20
	3,0 m	6XV1870-8GH30
	5,0 m	6XV1870-8GH50
	10,0 m	6XV1870-8GN10
PROFINET M12 trailable connecting cable, pre-assembled at one end with M12 connector, angled (one end plug, one end open cable)	3,0 m	3RK1902-2HB30
	5,0 m	3RK1902-2HB50
	10,0 m	3RK1902-2HC10
PROFINET M12 trailable connecting cable, pre-assembled at one end with M12 connector 180° (one end plug, one end with RJ45 Plug 145°)	2,0 m	6XV1871-5TH20
	3,0 m	6XV1871-5TH30
	5,0 m	6XV1871-5TH50
	10,0 m	6XV1871-5TN10
	15,0 m	6XV1871-5TN15

M12 cover caps		3RX9802-0AA00
M12 cover caps		3RK1901-1KA00
X1 P2 R (M12 socket)		
non-assembled connectors		
PROFINET M12 connector, d-coded with FastConnect system, 180°		
- 1 per pack		6GK1901-0DB20-6AA0
- 8 per pack		6GK1901-0DB20-6AA8
PROFINET M12 connector, d-coded with FastConnect system, 180°		
- 1 per pack		6GK1901-0DB10-6AA0
- 8 per pack		6GK1901-0DB10-6AA8
PROFINET M12 connector, d-coded, angled		3RK1902-2DA00
non-assembled cables		
PROFINET FC cable		
- FC TP Standard Cable		6XV1840-2AH10
- FC TP Trailing Cable		6XV1840-3AH10
- FC TP Trailing Cable GP		6XV1870-2D
- FC TP Marine Cable		6XV1840-4AH10
- FC TP Torsion Cable		6XV1870-2F
- FC TP Flexible Cable GP		6XV1870-2B
- FC TP FRNC Cable		6XV1871-2F
- FC TP Food Cable		6XV1871-2L
- FC TP Festoon Cable GP		6XV1871-2S
pre-assembled cables		
PROFINET M12 trailable connecting cable, pre-assembled at both ends with M12 connectors 180° (plug)	0,3 m	6XV1870-8AE30
	0,5 m	6XV1870-8AE50
	1,0 m	6XV1870-8AH10
	1,5 m	6XV1870-8AH15
	2,0 m	6XV1870-8AH20
	3,0 m	6XV1870-8AH30
	5,0 m	6XV1870-8AH50
	10,0 m	6XV1870-8AN10
	15,0 m	6XV1870-8AN15

PROFINET M12 trailable connecting cable, pre-assembled at both ends with M12 connectors angled (plug)	0,3 m	6XV1870-8GE30
	0,5 m	6XV1870-8GE50
	1,0 m	6XV1870-8GH10
	1,5 m	6XV1870-8GH15
	2,0 m	6XV1870-8GH20
	3,0 m	6XV1870-8GH30
	5,0 m	6XV1870-8GH50
	10,0 m	6XV1870-8GN10
	15,0 m	6XV1870-8GN15
PROFINET M12 trailable connecting cable, pre-assembled at one end with M12 connector, angled (one end plug, one end open cable)	3,0 m	3RK1902-2HB30
	5,0 m	3RK1902-2HB50
	10,0 m	3RK1902-2HC10
PROFINET M12 trailable connecting cable, pre-assembled at one end with M12 connector 180° (one end plug, one end with RJ45 Plug 145°)	2,0 m	6XV1871-5TH20
	3,0 m	6XV1871-5TH30
	5,0 m	6XV1871-5TH50
	10,0 m	6XV1871-5TN10
	15,0 m	6XV1871-5TN15
M12 cover caps		3RX9802-0AA00
M12 cover caps		3RK1901-1KA00
X1 P3 (RJ45)		
non-assembled connectors		
PROFINET RJ45 connector with FastConnect system, 180°		
- 1 per pack		6GK1901-1BB10-2AA0
- 10 per pack		6GK1901-1BB10-2AB0
PROFINET RJ45 connector with FastConnect system, angled		
- 1 per pack		6GK1901-1BB20-2AA0
- 10 per pack		6GK1901-1BB20-2AB0
pre-assembled cables		
Twisted-pair connecting cable 4x2 with RJ45 connector	0,5 m	6XV1870-3QE50
	1,0 m	6XV1870-3QH10
	2,0 m	6XV1870-3QH20
	6,0 m	6XV1870-3QH60
	10,0 m	6XV1870-3QN10
Crossed twisted-pair connecting cable 4x2 with RJ45 connectors	0,5 m	6XV1870-3RE50
	1,0 m	6XV1870-3RH10
	2,0 m	6XV1870-3RH20

	6,0 m	6XV1870-3RH60
	10,0 m	6XV1870-3RN10
X2 P1 (M12 socket)		
non-assembled connectors		
PROFINET M12 connector, d-coded w ith FastConnect system, 180°		
- 1 per pack		6GK1901-0DB20-6AA0
- 8 per pack		6GK1901-0DB20-6AA8
PROFINET M12 connector, d-coded w ith FastConnect system, 180°		
- 1 per pack		6GK1901-0DB10-6AA0
- 8 per pack		6GK1901-0DB10-6AA8
PROFINET M12 connector, d-coded, angled		3RK1902-2DA00
non-assembled cables		
PROFINET FC cable		
- FC TP Standard Cable		6XV1840-2AH10
- FC TP Trailing Cable		6XV1840-3AH10
- FC TP Trailing Cable GP		6XV1870-2D
- FC TP Marine Cable		6XV1840-4AH10
- FC TP Torsion Cable		6XV1870-2F
- FC TP Flexible Cable GP		6XV1870-2B
- FC TP FRNC Cable		6XV1871-2F
- FC TP Food Cable		6XV1871-2L
- FC TP Festoon Cable GP		6XV1871-2S
pre-assembled cables		
PROFINET M12 trailable connecting cable, pre-assembled at both ends w ith M12 connectors 180° (plug)	0,3 m	6XV1870-8AE30
	0,5 m	6XV1870-8AE50
	1,0 m	6XV1870-8AH10
	1,5 m	6XV1870-8AH15
	2,0 m	6XV1870-8AH20
	3,0 m	6XV1870-8AH30
	5,0 m	6XV1870-8AH50
	10,0 m	6XV1870-8AN10
	15,0 m	6XV1870-8AN15

PROFINET M12 trailable connecting cable, pre-assembled at both ends with M12 connectors angled (plug)	0,3 m	6XV1870-8GE30
	0,5 m	6XV1870-8GE50
	1,0 m	6XV1870-8GH10
	1,5 m	6XV1870-8GH15
	2,0 m	6XV1870-8GH20
	3,0 m	6XV1870-8GH30
	5,0 m	6XV1870-8GH50
	10,0 m	6XV1870-8GN10
	15,0 m	6XV1870-8GN15
PROFINET M12 trailable connecting cable, pre-assembled at one end with M12 connector, angled (one end plug, one end open cable)	3,0 m	3RK1902-2HB30
	5,0 m	3RK1902-2HB50
	10,0 m	3RK1902-2HC10
PROFINET M12 trailable connecting cable, pre-assembled at one end with M12 connector 180° (one end plug, one end with RJ45 Plug 145°)	2,0 m	6XV1871-5TH20
	3,0 m	6XV1871-5TH30
	5,0 m	6XV1871-5TH50
	10,0 m	6XV1871-5TN10
	15,0 m	6XV1871-5TN15
M12 cover caps		3RX9802-0AA00
M12 cover caps		3RK1901-1KA00
X3 DC 24V 7/8" (pin)		
non-assembled connectors		
7/8" conenctor 180° with socket insert		6GK1905-0FB00
7/8" connector angled with socket insert		3RK1902-3DA00
non-assembled cables		
Energy Cable, trailable, 5 x 1,5 mm ²		6XV1830-8AH10
pre-assembled cables		
7/8" connecting cable vor supplying trailable energy cable, 5 x 1,5 mm ² , pre-assembled at both ends with 7/8" connectors 180° (one end socket, one end pin)	0,3m	6XV1822-5BE30
	0,5m	6XV1822-5BE50
	1,0m	6XV1822-5BH10
	1,5 m	6XV1822-5BH15
	2,0 m	6XV1822-5BH20
	3,0 m	6XV1822-5BH30
	5,0 m	6XV1822-5BH50
	10,0 m	6XV1822-5BN10
	15,0 m	6XV1822-5BN15
7/8" connecting cable vor supplying trailable energy cable, 5 x 1,5 mm ² , pre-assembled at both ends with 7/8" connectors angled (one end socket, one end pin)	1,5 m	6XV1822-5BH15-OSB0 ¹⁾
	2,0 m	6XV1822-5BH20-OSB0 ¹⁾
	3,0 m	3RK1902-3NB30
	5,0 m	3RK1902-3NB50

	10,0 m	3RK1902-3NC10
	15,0 m	6XV1822-5BN15-0SB0 ¹⁾
7/8" connecting cable for supplying trailable energy cable, 5 x 1,5 mm ² , pre assembled at one end with 7/8" connector angled (one end socket, one end open cable)	3,0 m	3RK1902-3GB30
	5,0 m	3RK1902-3GB50
	10,0 m	3RK1902-3GC10
X4 DC 24V 7/8" (socket)		
non-assembled connectors		
7/8" connector 180° with pin insert		6GK1905-0FA00
7/8" connector angled with pin insert		3RK1902-3BA00
non-assembled cables		
Energy Cable, trailable, 5 x 1,5 mm ²		6XV1830-8AH10
pre-assembled cables		
7/8" connecting cable for supplying trailable energy cable, 5 x 1,5 mm ² , pre-assembled at both ends with 7/8" connectors 180° (one end socket, one end pin)	0,3m	6XV1822-5BE30
	0,5m	6XV1822-5BE50
	1,0m	6XV1822-5BH10
	1,5 m	6XV1822-5BH15
	2,0 m	6XV1822-5BH20
	3,0 m	6XV1822-5BH30
	5,0 m	6XV1822-5BH50
	10,0 m	6XV1822-5BN10
7/8" connecting cable for supplying trailable energy cable, 5 x 1,5 mm ² , pre-assembled at both ends with 7/8" connectors angled (one end socket, one end pin)	15,0 m	6XV1822-5BN15
	1,5 m	6XV1822-5BH15-0SB0 ¹⁾
	2,0 m	6XV1822-5BH20-0SB0 ¹⁾
	3,0 m	3RK1902-3NB30
	5,0 m	3RK1902-3NB50
7/8" cover caps	10,0 m	3RK1902-3NC10
	15,0 m	6XV1822-5BN15-0SB0 ¹⁾
		6ES7194-3JA00-0AA0

¹⁾ Ordering with ORG-ID: 10001539

