



Certificate of Compliance

Certificate: 1097907

Master Contract: 165071 (012730_C_000)

Project: 70116389

Date Issued: 2017-12-15

Issued to: Siemens AG
DF CP R&D VC 2
Werner-von-Siemens-Strasse 48
Amberg, 92224
GERMANY

The products listed below are eligible to bear the CSA Mark shown



Issued by: *Steven Montminy*
Steven Montminy

PRODUCTS

CLASS - C321103 - INDUSTRIAL CONTROL EQUIPMENT-Motor Controllers - Auxiliary Devices

22 mm auxiliary open-type devices:

- Contact Blocks and Lampholders, Cat. No. 3SB34, followed by 00, 03, 11, 20 or 23, followed by 0A, 0B, 0C, 0D, 0E, 0H, 0J, 0K, 0L, 0M, 0N, 0P, 0Q, 1A, 1B, 1C, 1D, 1F, 1G, 1H, 1J, 1L, 1PA, 1PB, 1PC, 1PD, 1PE, 1QA, 1QB, 1QC, 1QD, 1QE, 1RA, 1RB, 1RC, 1RD, 1RE, 3A, 3C, 3E, 3F, 3M, 3P or 3S, followed by a suffix of numbers and/or letters.
- Complete Push-button Units, Momentary, Non-Illuminated, Cat. No. 3SB3, followed by 2 or 6, followed 01, 02 or 03, followed by 0A, followed by A1, A2, A3, A4, A5 or A6, followed by a suffix of numbers and/or letters.
- Complete Push-button Units, Momentary, Non-Illuminated, Cat. No. 3SB33, followed by 01, 02 or 03, followed by 0A or 1H, followed by A1, A2, A3, A4, A5 or A6, followed by a suffix of numbers and/or letters.
- Complete Push-button Units, Momentary, Illuminated, Cat. No. 3SB3, followed by 2 or 6, followed by 05, 06, 07, 45, 46, 47, 50, 51, 53, 54, 55 or 57, followed by 0A, followed by A2, A3, A4, A5, A6 or A7, followed by a suffix of numbers and/or letters.
- Complete Push-button Units, Momentary, Illuminated, Cat. No. 3SB33, followed by 05, 06, 07, 45, 46, 47, 53, 54, 55 or 61, followed by 0A or 8B, followed by A2, A3, A4, A5, A6, A7 or C8, followed by a suffix of numbers and/or letters.
- Complete Push-button Units, Maintained, Cat. No. 3SB32, followed by 01 or 03, followed by 1C or 1H, followed by A2, followed by a suffix of numbers and/or letters.



Certificate: 1097907
Project: 70116389

Master Contract: 165071
Date Issued: 2017-12-15

- Complete Push-button Units, Maintained, Cat. No. 3SB36, followed by 01, 03 or 66, followed by 1C, 1H, 1T or 1X, followed by A2, P2 or R2, followed by a suffix of numbers and/or letters.
- Complete Selector Switch Units, Non-Illuminated and Complete Key-operated Switch Units, Cat. No. 3SB32, followed by 01, 02, 08 or 10, followed by 2D, 2E, 2K or 4A, followed by A1 or D1, followed by a suffix of numbers and/or letters.
- Complete Selector Switch Units, Non-Illuminated and Complete Key-operated Switch Units, Cat. No. 3SB36, followed by 01, 02, 08 or 10, followed by 2D, 2E, 2K, 2P, 2S, 2T or 4A, followed by A1 or D1, followed by 1, followed by a suffix of numbers and/or letters.
- Push-button Operators, Non-Illuminated, Cat. No. 3SB30, followed by 00, followed by 0A, 0B, 0C, 0D, 0E, 1B, 1C, 1D, 1E, 1G, 1H, 1K, 1L, 1M, 1X or 1Y, followed by A1, A2, A3, A4, A5, A6, A7, A8, B0, B1, B2 or B5, followed by a suffix of numbers and/or letters.
- Push-button Operators, Non-Illuminated, Cat. No. 3SB31, followed by 00 or 10, followed by 0A, 0D, 1B, 1H, 1K, 1L, 1M, 8A or 8C, followed by A1, A2, A3, A4, A5, A6, A7, C2 or C3, followed by a suffix of numbers and/or letters.
- Push-button Operators, Non-Illuminated, Cat. No. 3SB35, followed by 00 or 01, followed by 0A, 0B, 0D, 1B, 1C, 1D, 1E, 1G, 1H, 1K, 1L, 1M, 1Q, 1R, 1T, 1U or 1Y, followed by A1, A2, A3, A4, A5, A6, A7, A8, B0, B1, B2 or B5, followed by a suffix of numbers and/or letters.
- Push-button Operators, Illuminated, Cat. No. 3SB30, followed by 01, followed by 0A, 0B, 0D, 1C, 1D, 1E or 1G, followed by A2, A3, A4, A5, A6 or A7, followed by a suffix of numbers and/or letters.
- Push-button Operators, Illuminated, Cat. No. 3SB31, followed by 01 or 11, followed by 0A, 0D, 8B or 8D, followed by A2, A3, A4, A5, A6, A7, C2 or C3, followed by a suffix of numbers and/or letters.
- Push-button Operators, Illuminated, Cat. No. 3SB35, followed by 01, followed by 0A, 0B, 0D, 1C, 1D, 1E, 1G, 1Q or 1R, followed by A2, A3, A4, A5, A6 or A7, followed by a suffix of numbers and/or letters.
- Pilot Lights Operators, Cat. No. 3SB30, followed by 01, followed by 6A or 6B, followed by A2, A3, A4, A5, A6 or A7, followed by a suffix of numbers and/or letters.
- Pilot Light Operators, Cat. No. 3SB31, followed by 11, followed by 6A, followed by A2, A3, A4, A5, A6 or A7, followed by a suffix of numbers and/or letters.
- Pilot Light Operators, Cat. No. 3SB35, followed by 01, followed by 6A or 6B, followed by A1, A2, A3, A4, A5, A6 or A7, followed by a suffix of numbers and/or letters.
- Selector Switches Operators and Keyed Operators, Non-Illuminated, Cat. No. 3SB30, followed by 00, followed by 2D, 2E, 2F, 2G, 2K, 2L, 3A, 3B, 3D, 3E, 3F, 4A, 4B, 4D, 4E, 4F, 4G, 4H, 4L, 4M, 4P, 4Q, 4R, 4S, 5A, 5B, 5D, 5E, 5F, 5G, 5L, 5M, 5P, 5Q or 5R, followed by A1, A2, A4, A6, D0, D1, D2, D3, D4, D5, D6, E0, E1, E2, E3, E4, E5, E6, E7, F0, F1, F2, G0, G1, H0, H1, H2, J0, J1, K0, K1 or K2, followed by a suffix of numbers and/or letters.
- Selector Switches Operators and Keyed Operators, Non-Illuminated, Cat. No. 3SB31, followed by 10, followed by 2D, 2E, 2F, 2G, 2K, 2L, 3A, 3B, 3D, 4A, 4B, 4D, 4E, 4F, 4L, 4M, 4P, 4Q, 4R, 4S, 5A, 5B, 5F, 5L, 5M or 5Q, followed by A1, A2, A4, A6, D0, D1, D2, D4, D5, E0, E3, E4, E5, E7, F1, G0, G1, H0, H1, J0, J1, K0 or K1, followed by a suffix of numbers and/or letters.
- Selector Switches Operators and Keyed Operators, Non-Illuminated, Cat. No. 3SB35, followed by 00, followed by 2D, 2E, 2F, 2G, 2H, 2K, 2L, 2P, 2Q, 2S, 2T, 2U, 2V, 3A, 3B, 3D, 3E, 3F, 3G, 3H, 3P, 3S, 3T, 3U, 3V, 4A, 4B, 4D, 4E, 4F, 4G, 4L, 4M, 4P, 4Q, 4R, 4S, 5A, 5B, 5D, 5E, 5F, 5G, 5L, 5M, 5P, 5Q, 5R or 5S, followed by A1,



Certificate: 1097907
Project: 70116389

Master Contract: 165071
Date Issued: 2017-12-15

A2, A4, A6, D0, D1, D2, D3, D4, D5, D6, E0, E1, E2, E3, E4, E5, E6, E7, F0, F1, F2, G0, G1, G2, G3, G4, H0, H1, H2, H3, H4, J0, J1, J2, J3, J4, K0, K1, K2, K3, K4 or P1, followed by a suffix of numbers and/or letters.

- Selector Switches Operators and Keyed Operators, Illuminated, Cat. No. 3SB30, followed by 01, followed by 2D, 2E, 2K or 2L, followed by A2, A3, A4, A5 or A7, followed by a suffix of numbers and/or letters.
- Selector Switches Operators and Keyed Operators, Illuminated, Cat. No. 3SB31, followed by 11, followed by 2D, 2E, 2K or 2L, followed by A2, A3, A4, A5 or A7, followed by a suffix of numbers and/or letters.
- Selector Switches Operators and Keyed Operators, Illuminated, Cat. No. 3SB35, followed by 01, followed by 2D, 2E, 2K, 2L, 2P, 2Q, 2T, 2S, 3P, 3Q, 3S or 3T, followed by A2, A3, A4, A5 or A7, followed by a suffix of numbers and/or letters.
- Support Terminals, open type, Types 3SB3901-0AG, -0AH and -0AJ, rated 20A, 600V.
- Potentiometer, Cat. No. 3SB1000-7CH07 or 3SB1000-7CJ07.
- Illuminated backplate for E-Stop, Cat. No. 3SB3921-0DA.
- Accessories, Types 3SB followed by 19, 29, 39 followed by a suffix of letters and/or numbers.
- Accessories, Types 3SX and 3SY followed by a suffix of numbers.

Ratings:

- Contact Blocks: A600, R300 ; for A600, same polarity
- Contact Blocks, Type 3SB3400-0M: A300, Q300.
- Pilot Light Units (Suffix 1A, -1D, 1N): 125V ac/dc, 2.5W max.
- Pilot Lights Units (Suffixes 1B, 1C and 1F): 240V ac, only with bulb 130V, max 2.6W.
- Pilot Lights Units (Suffixes 1G, 1H or 1L): 6 to 125 V ac/dc. Only with bulb rated 2.6W.
- Pilot Lights Transformers (Suffix 3): 127V ac, 240V ac, 260 V ac, 400V ac, 480V ac or 600V ac primary; 6V or 24V secondary.
- Pilot Lights Units (Suffix 1R, 1P or 1Q): LED 24V ac/dc, 110 and 230V ac.
- Illuminated backplate for E-Stop, Cat. No. 3SB3921-0DA: 24V ac/dc.
- Environmental designation for actuators and lenses: Types 1, 3, 4, 4X and 12K.
- Environmental designation for potentiometer: Types 1, 4 (Indoor) and 12.
- Environmental designation for illuminated backplate, Cat. No. 3SB3921-0DA: Types 1, 4 (Indoor) and 12.
- Environmental designation for blanking plugs, Cat. Nos. 3SB1902, 3SB3921, 3SB3941: Types 1, 4 (Indoor) and 12.

Notes:

- a) Open-type devices are Certified only for use in complete assemblies where the suitability of the combination is subject to further investigation.
- b) The Cat. No. designation is followed by a suffix of numbers and/or letters for manufacture use only.

APPLICABLE REQUIREMENTS

- | | | |
|--------------------------|---|------------------------------|
| CSA-C22.2 No. 14-13 | - | Industrial Control Equipment |
| CAN/CSA-C22.2 No. 94-M91 | - | Special Purpose Enclosures |