

Molded Case Circuit Breakers

ND-Frame Sentron™ Series Circuit Breaker

2 & 3-Pole; 800-1200 Amperes



Ratings & Markings (UL 489 AIR Interrupting Ratings)

Breaker Type	RMS Symmetrical Amperes (kA)						Frame Only		
	Volts AC (50/60Hz)			Volts DC					
	240	480	600	250	500		Breaker Type	Frame (2-Pole)	Frame (3-Pole)
ND6, NXD6	65	50	25	30 (2-P)	25 (3-P)		ND6	ND62F120	ND63F120
HND6, HNXD6	100	65	50	30 (2-P)	50 (3-P)		HND6	—	HND63F120
CND6	200	100	65	—	50 (3-P)		—	—	—

Dimensions

Breaker Type	Length	Width	Depth	D-1 (to handle)
ND6, NXD6, HND6, HNXD6, CND6	16 in.	9 in.	6 in.	8.25 in.
With NDTS lug shield	24 in.	9 in.	6 in.	8.25 in.

Frames

Trip Amperage	Poles	Breaker-Type Non-interchangeable Trip		Breaker-Type Interchangeable Trip		Trip Unit Only
		NXD6	HNXD6	HND6	ND6	ND6
800	2	—	—	—	ND62B800	MD62T800
900	2	NXD62B900	—	—	ND62B900	ND62T900
1000	2	NXD62B100	—	—	ND62B100	ND62T100
1200	2	NXD62B120	—	—	ND62B120	ND62T120
800	3	—	—	HND63B800	ND63B800	MD63T800
900	3	NXD63B900	HNXD63B900	HND63B900	ND63B900	ND63T900
1000	3	NXD63B100	HNXD63B100	HND63B100	ND63B100	ND63T100
1140	3	NXD63B114	HNXD63B114	—	—	—
1200	3	NXD63B120	HNXD63B120	HND63B120	ND63B120	ND63T120

Frames - Molded Case Switch - Circuit Disconnect

Ampere Rating	Poles	NXD6	CND6
1200	3	NXD63S120A	CND63S120A

Lugs For 75°C Wire

Catalog Number	Cables Per Lug	Wire Range
TA2K500	2	#1-500 kcmil Cu/Al
TA3K500	3	#1-500 kcmil Cu/Al
TC2K500	2	#1-500 kcmil Cu
TC3K350	3	#1-350 kcmil Cu
Kits (2 Kits required per breaker)		
2TA4P8500 3TA4P8500	4	250–500 kcmil Cu/Al
2TA4N8500 3TA4N8500	4	250–500 kcmil Cu/Al
2TA2N8750 3TA2N8750	2	500–750 kcmil Cu/Al
2TA3N8750 3TA3N8750	3	500–750 kcmil Cu/Al

Shunt Trip Combinations

Control Voltage		1 Shunt Trip	1 Shunt Trip and 1 Auxiliary Switch
AC	DC	Catalog Number	Catalog Number
120	—	S01MN6	S01MN64A
208	—	S02MN6	—
240	—	S03MN6	S03MN64A
277	—	S15MN6	S15MN64A
480	—	S04MN6	S04MN64A
600	—	S06MN6	—
—	12	S16MN6	S16MN64A
—	24	S07MN6	S07MN64A
—	48	S09MN6	—
—	125	S11MN6	S11MN64A
—	250	S13MN6	S13MN64A

Auxiliary Switch Combinations

Maximum Voltage		1 Form C	2 Form C
AC	DC	Catalog Number	Catalog Number
480	250	A01MN64	A02MN64
—	12	A01MNDLV	A02MNDLV

Alarm Switch Combinations

Maximum Voltage		1 Alarm Switch	1 Alarm Switch and 1 Auxiliary Switch	1 Alarm Switch and 2 Auxiliary Switches
AC	DC	Catalog Number	Catalog Number	Catalog Number
480	250	B00MN64	A01MN64B	A02MN64B

Undervoltage Trip Combinations

Control Voltage		1 Undervoltage Trip	1 Undervoltage Trip and 1 Auxiliary Switch	1 Undervoltage Trip and 2 Auxiliary Switches
AC	DC	Catalog Number	Catalog Number	Catalog Number
120	—	U01MN6	U01MN64A	U01MN64AA
208	—	U02MN6	U02MN64A	U02MN64AA
240	—	U03MN6	U03MN64A	U03MN64AA
277	—	U15MN6	U15MN64A	U15MN64AA
480	—	U04MN6	U04MN64A	U04MN64AA
600	—	U06MN6	—	—
—	24	U07MN6	U07MN64A	U07MN64AA
—	48	U09MN6	U09MN64A	U09MN64AA
—	125	U11MN6	U11MN64A	U11MN64AA
—	250	U13MN6	U13MN64A	U13MN64AA

Legal Manufacturer

Siemens Industry, Inc.
3617 Parkway Ln
Peachtree Corners, GA 30092
United States of America

Telephone: +1 (800) 333-7421
www.usa.siemens.com/circuitbreakers

Order No. CBDS-NDGEN-1122
© 11.2022, Siemens Industry, Inc.

This document contains a general description of available technical options only, and its effectiveness will be subject to specific variables including field conditions and project parameters. Siemens does not make representations, warranties, or assurances as to the accuracy or completeness of the content contained herein. Siemens reserves the right to modify the technology and product specifications in its sole discretion without advance notice.