

UK Declaration of Conformity

No. 666.MNER.BF.40.2107.002

Manufacturer: Siemens AG, DI MC
Address: Frauenausracher Straße 80
91056 Erlangen
Germany

UK importer: Siemens plc
UK importer address: Manchester
M20 2UR
United Kingdom

Product Family: SINAMICS Options

The indicated product family placed on the market by us is in conformance to the regulations of the following UK Regulations:

Supply of Machinery (Safety) Regulations 2008

+ Related amendments

More details regarding adherence to this Regulation is provided in Appendix MD.

Electrical Equipment (Safety) Regulations 2016

+ Notice of Publication 0009/21

More details regarding adherence to this Regulation is provided in Appendix LVD.

Electromagnetic Compatibility Regulations 2016

+ Notice of Publication 0007/21

More details regarding adherence to this Regulation is provided in Appendix EMC.

The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012

+ Notice of Publication 0037/21

More details regarding adherence to this Regulation is provided in Appendix RoHS.

This declaration of conformity is issued under the sole responsibility of the manufacturer.

Erlangen, 21-07-26

X 

i.V. D. Vielsäcker
Head of Test, Processes & Architecture
Signiert von: Vielsaecker Dirk

X 

i.V. T. Heinzelmänn
Head of Quality Management
Signiert von: Heinzelmänn Thomas

Appendix MD

to UK Declaration of Conformity

No. 666.MNER.BF.40.2107.002

Product family: **SINAMICS Options**

Conformity of the products designated below with the Supply of Machinery (Safety) Regulations 2008 is verified by adherence to the following standards.

Reference number: **Edition:**

EN 61800-5-2 **2007**

This standard implicitly includes the related product standard EN 61800-5-1 for all modules listed under Machinery Directive that are also subject to the Low Voltage Regulation.

The person authorized to compile the technical documents is the responsible Functional Safety Manager of Siemens AG, DI MC.

The components of the product family to which the UK marking applies are given in the Appendix "Component List".

Appendix LVD

to UK Declaration of Conformity

No. 666.MNER.BF.40.2107.002

Product family: **SINAMICS Options**

Conformity of the products designated below with the Electrical Equipment (Safety) Regulations 2016 is verified by adherence to the following standards:

Reference number: **Edition:**

EN 61800-5-1 **2007**

The components of the product family to which the UK marking applies are given in the Appendix "Component List".

Appendix EMC

to UK Declaration of Conformity

No. 666.MNER.BF.40.2107.002

Product family: **SINAMICS Options**

Conformity of the products designated below with the Electromagnetic Compatibility Regulations 2016 is verified by adherence to the following standards:

Reference number: **Edition:**

EN IEC 61800-3 **2004+A1:2012**

The components of the product family to which the UK marking applies are given in the Appendix "Component List".

Appendix RoHS

to UK Declaration of Conformity

No. 666.MNER.BF.40.2107.002

Product family: **SINAMICS Options**

Conformity of the products designated below with the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 is verified by adherence to the following standards:

Reference number: **Edition:**

EN IEC 63000 **2018**

The components of the product family to which the UK marking applies are given in the Appendix "Component List".

Appendix Component List to UK Declaration of Conformity

No. 666.MNER.BF.40.2107.002

The value in column Electrical Equipment
(Safety) marks the year of first placing on the
market.

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
Active Interface Module						
AIM (ALM, 3AC, 380-480V, 16kW)	6SL3100-0BE21-6AB0	FILTER	---	X	X	X
AIM (ALM, 3AC, 380-480V, 36kW)	6SL3100-0BE23-6AB0	FILTER	---	X	X	X
AIM (ALM, 3AC, 380-480V, 55kW)	6SL3100-0BE25-5AB0	FILTER	---	X	X	X
AIM (ALM, 3AC, 380-480V, 80kW)	6SL3100-0BE28-0AB0	FILTER	---	X	X	X
AIM (ALM, 3AC, 380-480V, 120kW)	6SL3100-0BE31-2AB0	FILTER	---	X	X	X
AIM (ALM, 3AC, 380-480V, 160kW)	6SL3300-7TE32-6AA1	FILTER	---	X	X	X
AIM (GG, 3AC, 380-480V, 260A)	6SL3300-7TE32-6AB1	FILTER	---	X	X	X
AIM (ALM, 3AC, 380-480V, 235kW)	6SL3300-7TE33-8AA1	FILTER	---	X	X	X
AIM (GG, 3AC, 380-480V, 380A)	6SL3300-7TE33-8AB1	FILTER	---	X	X	X
AIM (ALM, 3AC, 380-480V, 300kW)	6SL3300-7TE35-0AA1	FILTER	---	X	X	X
AIM (GG, 3AC, 380-480V, 490A)	6SL3300-7TE35-0AB1	FILTER	---	X	X	X
AIM (ALM, 3AC, 380-480V, 500kW)	6SL3300-7TE38-4AA1	FILTER	---	X	X	X
AIM (ALM, 3AC, 380-480V, 900kW)	6SL3300-7TE41-4AA1	FILTER	---	X	X	X
AIM (GG, 3AC, 380-480V, 1405A)	6SL3300-7TE41-4AC1	FILTER	---	X	X	X
AIM (GG, 3AC, 500-690V, 145A)	6SL3300-7TG31-4AB1	FILTER	---	X	X	X
AIM (GG, 3AC, 500-690V, 310A)	6SL3300-7TG33-1AB1	FILTER	---	X	X	X
AIM (ALM, 3AC, 500-690V, 630kW)	6SL3300-7TG35-8AA1	FILTER	---	X	X	X
AIM (ALM, 3AC, 500-690V, 800kW)	6SL3300-7TG37-4AA1	FILTER	---	X	X	X
AIM (GG, 3AC, 500-690V, 735A)	6SL3300-7TG37-4AC1	FILTER	---	X	X	X
AIM (ALM, 3AC, 500-690V, 1400kW)	6SL3300-7TG41-3AA1	FILTER	---	X	X	X
AIM (GG, 3AC, 500-690V, 1270A)	6SL3300-7TG41-3AC1	FILTER	---	X	X	X
AIM (ALM, 3AC, 500-690V, 1400kW)	6SL3300-7TG41-3AW1	FILTER	---	X	X	X
AIM (Chassis, 3AC, 380-480V, 400kW)	6SL3301-7TE36-4AA0	FILTER	---	X	X	X
AIM (Chassis, 3AC, 380-480V, 630kW)	6SL3301-7TE41-0AA0	FILTER	---	X	X	X
AIM (Chassis, 3AC, 380-480V, 900kW)	6SL3301-7TE41-4AA0	FILTER	---	X	X	X
AIM (ALM, 3AC, 380-480V, 500kW)	6SL3305-7TE38-4AA5	FILTER	---	X	X	X
AIM (ALM, 3AC, 380-480V, 900kW)	6SL3305-7TE41-4AA5	FILTER	---	X	X	X
AIM (ALM, 3AC, 380-480V, 900kW)	6SL3305-7TE41-4AA7	FILTER	---	X	X	X
AIM (ALM, 3AC, 500-690V, 800kW)	6SL3305-7TG37-4AA5	FILTER	---	X	X	X
AIM (ALM, 3AC, 500-690V, 1100kW)	6SL3305-7TG41-0AA5	FILTER	---	X	X	X
AIM (ALM, 3AC, 500-690V, 1100kW)	6SL3305-7TG41-0AA7	FILTER	---	X	X	X
AIM (ALM, 3AC, 500-690V, 1400kW)	6SL3305-7TG41-3AA5	FILTER	---	X	X	X
AIM (ALM, 3AC, 500-690V, 1400kW)	6SL3305-7TG41-3AA7	FILTER	---	X	X	X
AIM (ALM, 3AC, 500-690V, 1700kW)	6SL3305-7TG41-6AA5	FILTER	---	X	X	X

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Klaus Helmrich, Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The value in column Electrical Equipment (Safety) marks the year of first placing on the market.

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
AIM (ALM, 3AC, 500-690V, 1700kW)	6SL3305-7TG41-6AA7	FILTER	---	X	X	X
AIM+ALM (Chassis, 3AC, 380-480V, 355kW)	6SL3341-7TE35-6AA0	FILTER	---	X	X	X
AIM+ALM (Chassis, 3AC, 380-480V, 400kW)	6SL3341-7TE36-4AA0	FILTER	---	X	X	X
AIM+ALM (Chassis, 3AC, 380-480V, 450kW)	6SL3341-7TE37-5AA0	FILTER	---	X	X	X
AIM+ALM (Chassis, 3AC, 380-480V, 500kW)	6SL3341-7TE38-4AA0	FILTER	---	X	X	X
AIM+ALM (Chassis, 3AC, 380-480V, 530kW)	6SL3341-7TE38-8AA0	FILTER	---	X	X	X
AIM+ALM (Chassis, 3AC, 380-480V, 630kW)	6SL3341-7TE41-0AA0	FILTER	---	X	X	X
AIM+ALM (Chassis, 3AC, 380-480V, 710kW)	6SL3341-7TE41-2AA0	FILTER	---	X	X	X
AIM+ALM (Chassis, 3AC, 380-480V, 800kW)	6SL3341-7TE41-3AA0	FILTER	---	X	X	X
AIM+ALM (Chassis, 3AC, 380-480V, 900kW)	6SL3341-7TE41-4AA0	FILTER	---	X	X	X
Active Line Filter						
Basic Line Filter						
Basic Line Filter (16kW)	6SL3000-0BE21-6DA0	FILTER	---	X	---	X
Basic Line Filter (36kW)	6SL3000-0BE23-6DA1	FILTER	---	X	---	X
Basic Line Filter (55kW)	6SL3000-0BE25-5DA0	FILTER	---	X	---	X
Basic Line Filter (80kW)	6SL3000-0BE28-0DA0	FILTER	---	X	---	X
Basic Line Filter (120kW)	6SL3000-0BE31-2DA0	FILTER	---	X	---	X
Line Filter						
Line Filter (PX, 3AC, 380-480V, 250A)	6SL3000-0BE32-5AA0	FILTER	---	X	---	X
Line Filter (PX, 3AC, 380-480V, 400A)	6SL3000-0BE33-1AA0	FILTER	---	X	---	X
Line Filter (PX, 3AC, 380-480V, 440A)	6SL3000-0BE34-4AA0	FILTER	---	X	---	X
Line Filter (PX, 3AC, 380-480V, 600A)	6SL3000-0BE35-0AA0	FILTER	---	X	---	X
Line Filter (PX, 3AC, 380-480V, 600A)	6SL3000-0BE36-0AA0	FILTER	---	X	---	X
Line Filter (3AC, 380-480V, 1200A)	6SL3000-0BE41-2AA0	FILTER	---	X	---	X
Line Filter (3AC, 380-480V, 1600A)	6SL3000-0BE41-6AA0	FILTER	---	X	---	X
Line Filter (3AC, 500-690V, 250A)	6SL3000-0BG32-5AA0	FILTER	---	X	---	X
Line Filter (3AC, 500-690V, 440A)	6SL3000-0BG34-4AA0	FILTER	---	X	---	X
Line Filter (3AC, 500-690V, 600A)	6SL3000-0BG36-0AA0	FILTER	---	X	---	X
Line Filter (3AC, 500-690V, 1200A)	6SL3000-0BG41-2AA0	FILTER	---	X	---	X
Line Filter (3AC, 660-690V, 1600A)	6SL3000-0BG41-6AA0	FILTER	---	X	---	X
Line Filter (SLM, 5kW, 3AC, 380-480V)	6SL3000-0HE15-0AA0	FILTER	---	X	---	X
Line Filter (SLM, 10kW, 3AC, 380-480V)	6SL3000-0HE21-0AA0	FILTER	---	X	---	X
Line Filter (3AC, 380-480V, 160/200/250/315kW)	6SL3000-0JE36-1AA0	FILTER	---	X	---	X
Line Filter (3AC, 380-480V, 400/450kW)	6SL3000-0JE38-4AA0	FILTER	---	X	---	X
Line Filter (3AC, 380-480V, 560kW)	6SL3000-0JE41-0AA0	FILTER	---	X	---	X
Line Filter (3AC, 500-600V, 110/132/160/200kW)	6SL3000-0JH33-3AA0	FILTER	---	X	---	X
Line Filter (3AC, 500-600V, 250/315kW)	6SL3000-0JH34-7AA0	FILTER	---	X	---	X
Line Filter (3AC, 500-600V, 400kW)	6SL3000-0JH35-8AA0	FILTER	---	X	---	X
Line Filter (3AC, 500-600V, 500/560kW)	6SL3000-0JH38-1AA0	FILTER	---	X	---	X
C2-Filter (V70/V90, 1AC, 200-240V, 18A)	6SL3203-0BB21-8VA0	FILTER	---	X	---	X
C2-Filter (S210, 1AC, 200-240V, 18A)	6SL3203-0BB21-8VA1	FILTER	---	X	---	X

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Klaus Helmrich, Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The value in column Electrical Equipment (Safety) marks the year of first placing on the market.

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
Line Filter (FSC, 3AC, 380-480V, 39.4A)	6SL3203-0BD23-8SA0	FILTER	---	X	---	X
C2-Filter (V70/V90, 3AC, 200-480V, 5A)	6SL3203-0BE15-0VA0	FILTER	---	X	---	X
Line Filter (FSA, 3AC, 380-480V, 11.4A)	6SL3203-0BE17-7BA0	FILTER	---	X	---	X
Line Filter (FSA, 3AC, 380-480V, 11.4A)	6SL3203-0BE17-7BA1	FILTER	---	X	---	X
C2-Filter (V70/V90, 3AC, 200-480V, 12A)	6SL3203-0BE21-2VA0	FILTER	---	X	---	X
Line Filter (FSB, 3AC, 380-480V, 10.2A)	6SL3203-0BE21-6SA0	FILTER	---	X	---	X
Line Filter (FSB, 3AC, 380-480V, 23.5A)	6SL3203-0BE21-8BA0	FILTER	---	X	---	X
C2-Filter (V70/V90, 3AC, 200-480V, 20A)	6SL3203-0BE22-0VA0	FILTER	---	X	---	X
C2-Filter (S210, 3AC, 380-480V, 35A)	6SL3203-0BE23-5HA0	FILTER	---	X	---	X
Line Filter (FSC, 3AC, 380-480V, 49.4A)	6SL3203-0BE23-8BA0	FILTER	---	X	---	X
C2-Filter (S210, 3AC, 380-480V, 65A)	6SL3203-0BE26-5HA0	FILTER	---	X	---	X
Line Filter (FSD, 3AC, 380-480V, 72.0A)	6SL3203-0BE27-5BA0	FILTER	---	X	---	X
Line Filter (FSE, 3AC, 380-480V, 105.0A)	6SL3203-0BE31-1BA0	FILTER	---	X	---	X
Line Filter (FSF, 3AC, 380-480V, 204.0A)	6SL3203-0BE31-8BA0	FILTER	---	X	---	X
Line Filter (FSF, 3AC, 380-480V, 250.0A)	6SL3203-0BE32-5AA0	FILTER	---	X	---	X
Line Filter (3AC, 380-480V, 840A)	6SL3760-0MB00-0AA0	SPARE PART	---	X	---	X
Line Filter (3AC, 380-480V, 1405A)	6SL3760-0MC00-0AA0	SPARE PART	---	X	---	X
Line Filter (3AC, 440V, 310A)	6SL3760-0MD00-0AA0	SPARE PART	---	X	---	X
Line Filter (3AC, 500-690V, 600A)	6SL3760-0ME00-0AA0	SPARE PART	---	X	---	X
Line Filter (3AC, 500-690V, 1270A)	6SL3760-0MG00-0AA0	SPARE PART	---	X	---	X
Line Filter (760V, 50A)	6SL3760-0MM00-0AA0	SPARE PART	---	X	---	X
Line Filter (3AC, 500-690V, 1025A)	6SL3760-0MN00-0AA0	SPARE PART	---	X	---	X
Line Filter (520V, 36A)	6SL3760-0MP00-0AA0	SPARE PART	---	X	---	X
Line Filter (3AC, 380-480V, 1200A)	6SL3760-0MR00-0AA0	SPARE PART	---	X	---	X
Line Filter (3AC, 500-690V, 1200A)	6SL3760-0MS00-0AA0	SPARE PART	---	X	---	X
Sine Filter						
Sine Filter (PX, 3AC, 380-480V, 225A)	6SL3000-2CE32-3AA0	FILTER	---	X	---	X
Sine Filter (PX, 3AC, 380-480V, 276A)	6SL3000-2CE32-8AA0	FILTER	---	X	---	X
Sine Filter (PX, 3AC, 380-480V, 333A)	6SL3000-2CE33-3AA0	FILTER	---	X	---	X
Sine Filter (PX, 3AC, 380-480V, 408A)	6SL3000-2CE34-1AA0	FILTER	---	X	---	X
Sine Filter (3AC, 3AC, 500-600V, 188A)	6SL3000-2CF31-7AA0	SPARE PART	---	X	---	X
Sine Filter (FSA, 3AC, 380-480V, 3.5A)	6SL3202-0AE20-3SA0	FILTER	---	X	---	X
Sine Filter (FSA, 3AC, 380-480V, 6.0A)	6SL3202-0AE20-6SA0	FILTER	---	X	---	X
Sine Filter (FSB, 3AC, 380-480V, 9.0A)	6SL3202-0AE21-1SA0	FILTER	---	X	---	X
Sine Filter (FSB, 3AC, 380-480V, 14.0A)	6SL3202-0AE21-4SA0	FILTER	---	X	---	X
Sine Filter (FSC, 3AC, 380-480V, 20.0A)	6SL3202-0AE22-0SA0	FILTER	---	X	---	X
Sine Filter (FSC, 3AC, 380-480V, 33.0A)	6SL3202-0AE23-3SA0	FILTER	---	X	---	X
Sine Filter (FSD, 3AC, 380-480V, 47.0A)	6SL3202-0AE24-6SA0	FILTER	---	X	---	X
Sine Filter (FSD, 3AC, 380-480V, 61.8A)	6SL3202-0AE26-2SA0	FILTER	---	X	---	X
Sine Filter (FSE, 3AC, 380-480V, 92.0A)	6SL3202-0AE28-8SA0	FILTER	---	X	---	X
Sine Filter (FSF, 3AC, 380-480V, 150.0A)	6SL3202-0AE31-5SA0	FILTER	---	X	---	X

The value in column Electrical Equipment (Safety) marks the year of first placing on the market.

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
Sine Filter (FSF, 3AC, 380-480V, 182.0A)	6SL3202-0AE31-8SA0	FILTER	---	X	---	X
dv/dt Filter						
dv/dt Filter (3AC, 380-480V, 132kW)	6SL3000-2DE32-6AA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 380-480V, 110/132kW)	6SL3000-2DE32-6EA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 380-480V, 250kW)	6SL3000-2DE35-0AA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 380-480V, 160/200/250kW)	6SL3000-2DE35-0EA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 380-480V, 450kW)	6SL3000-2DE38-4AA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 380-480V, 315/400/450kW)	6SL3000-2DE38-4EA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 380-480V, 800kW)	6SL3000-2DE41-4AA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 380-480V, 560/710/800kW)	6SL3000-2DE41-4EA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 75/90kW)	6SL3000-2DG31-0EA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 110/132kW)	6SL3000-2DG31-5EA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 110/132kW)	6SL3000-2DG32-2EA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 160/200kW)	6SL3000-2DG33-3EA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 250kW)	6SL3000-2DG34-1EA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 315/400kW)	6SL3000-2DG35-8EA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 500/560kW)	6SL3000-2DG38-1EA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 900/1000/1200kW)	6SL3000-2DG41-3EA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 90kW)	6SL3000-2DH31-0AA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 132kW)	6SL3000-2DH31-5AA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 200kW)	6SL3000-2DH32-2AA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 315kW)	6SL3000-2DH33-3AA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 400kW)	6SL3000-2DH34-1AA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 560kW)	6SL3000-2DH35-8AA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 800kW)	6SL3000-2DH38-1AA0	FILTER	---	X	---	X
dv/dt Filter (3AC, 500-690V, 1200kW)	6SL3000-2DH41-3AA0	FILTER	---	X	---	X
Line Reactor						
Line Reactor (SLM, 5kW)	6SL3000-0CE15-0AA0	REACTOR	---	X	---	X
Line Reactor (SLM, 10kW)	6SL3000-0CE21-0AA0	REACTOR	---	X	---	X
Line Reactor (SLM, 16kW)	6SL3000-0CE21-6AA0	REACTOR	---	X	---	X
Line Reactor (BLM, 20kW)	6SL3000-0CE22-0AA0	REACTOR	---	X	---	X
Line Reactor (SLM, 36kW)	6SL3000-0CE23-6AA0	REACTOR	---	X	---	X
Line Reactor (BLM, 40kW)	6SL3000-0CE24-0AA0	REACTOR	---	X	---	X
Line Reactor (SLM, 55kW)	6SL3000-0CE25-5AA0	REACTOR	---	X	---	X
Line Reactor (BLM, 100kW)	6SL3000-0CE31-0AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 225A)	6SL3000-0CE32-3AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 278A)	6SL3000-0CE32-8AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 332A)	6SL3000-0CE33-3AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 509A)	6SL3000-0CE35-1AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 628A)	6SL3000-0CE36-3AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 773A)	6SL3000-0CE37-7AA0	REACTOR	---	X	---	X

The value in column Electrical Equipment (Safety) marks the year of first placing on the market.

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
Line Reactor (3AC, 380-480V, 871A)	6SL3000-0CE38-7AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 1022A)	6SL3000-0CE41-0AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 1458A)	6SL3000-0CE41-5AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 1600A)	6SL3000-0CE41-6AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 660-690V, 107A)	6SL3000-0CH31-1AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 660-690V, 154A)	6SL3000-0CH31-6AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 660-690V, 223A)	6SL3000-0CH32-2AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 660-690V, 270A)	6SL3000-0CH32-7AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 660-690V, 342A)	6SL3000-0CH33-4AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 660-690V, 482A)	6SL3000-0CH34-8AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 660-690V, 597A)	6SL3000-0CH36-0AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 660-690V, 840A)	6SL3000-0CH38-4AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 660-690V, 1167A)	6SL3000-0CH41-2AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 660-690V, 1600A)	6SL3000-0CH41-6AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 16kW)	6SL3000-0DE21-6AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 36kW)	6SL3000-0DE23-6AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 55kW)	6SL3000-0DE25-5AA1	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 80kW)	6SL3000-0DE28-0AA1	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 120kW)	6SL3000-0DE31-2AA1	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 355kW)	6SL3000-0EE36-2AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 500kW)	6SL3000-0EE38-8AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 800kW)	6SL3000-0EE41-4AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 500-690V, 450kW)	6SL3000-0EH34-7AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 500-690V, 710kW)	6SL3000-0EH37-6AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 500-690V, 1400kW)	6SL3000-0EH41-4AA0	REACTOR	---	X	---	X
Line Reactor (COMBI, 3AC, 380-480V, 16kW)	6SL3100-0EE21-6AA0	REACTOR	---	X	---	X
Line Reactor (COMBI, 3AC, 380-480V, 20kW)	6SL3100-0EE22-0AA0	REACTOR	---	X	---	X
Line Reactor (FSB, 3AC, 380-480V, 10A)	6SL3203-0CD21-0AA0	REACTOR	---	X	---	X
Line Reactor (FSB, 3AC, 200-480V, 14A)	6SL3203-0CD21-4AA0	REACTOR	---	X	---	X
Line Reactor (FSC, 3AC, 380-480V, 22A)	6SL3203-0CD22-2AA0	REACTOR	---	X	---	X
Line Reactor (FSC, 3AC, 200-480V, 35A)	6SL3203-0CD23-5AA0	REACTOR	---	X	---	X
Line Reactor (FSD, 3AC, 220-480V, 63A)	6SL3203-0CD25-3AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 4.0A)	6SL3203-0CE13-2AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 11.3A)	6SL3203-0CE21-0AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 22.3A)	6SL3203-0CE21-8AA0	REACTOR	---	X	---	X
Line Reactor (3AC, 380-480V, 47.4A)	6SL3203-0CE23-8AA0	REACTOR	---	X	---	X
Line Reactor (FSD, 3AC, 380-600V, 47A)	6SL3203-0CJ24-5AA0	REACTOR	---	X	---	X
Line Reactor (FSE, 3AC, 380-600V, 94A)	6SL3203-0CJ28-6AA0	REACTOR	---	X	---	X
DC Smoothing Filter						
DC Link Filter (55kW)	6SL3100-0DC25-5AA0	REACTOR	---	X	---	X
DC Link Filter (120kW)	6SL3100-0DC31-2AA0	REACTOR	---	X	---	X

The value in column Electrical Equipment (Safety) marks the year of first placing on the market.

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
DC Link Filter (booksize)	6SL3100-1DC01-0AA0	CAP MODULE	---	x	---	x
DC Link Filter (top hat rail)	6SL3100-1DC02-0AA0	CAP MODULE	---	x	---	x
Motor Reactor						
Motor Reactor (3AC, 380-480V, 315kW)	6SL3000-2AE36-1AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 380-480V, 400/450kW)	6SL3000-2AE38-4AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 380-480V, 560kW)	6SL3000-2AE41-0AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 380-480V, 710/800kW)	6SL3000-2AE41-4AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 660-690V, 85/100A)	6SL3000-2AH31-0AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 660-690V, 120/150A)	6SL3000-2AH31-5AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 660-690V, 175A)	6SL3000-2AH31-8AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 660-690V, 215A)	6SL3000-2AH32-4AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 660-690V, 260A)	6SL3000-2AH32-6AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 500-690V, 315kW)	6SL3000-2AH33-6AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 500-690V, 400kW)	6SL3000-2AH34-5AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 500-690V, 450kW)	6SL3000-2AH34-7AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 500-690V, 560kW)	6SL3000-2AH35-8AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 500-690V, 710/800kW)	6SL3000-2AH38-1AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 500-690V, 900kW)	6SL3000-2AH41-0AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 500-690V, 1000kW)	6SL3000-2AH41-1AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 500-690V, 1200kW)	6SL3000-2AH41-3AA0	REACTOR	---	x	---	x
Motor Reactor (Booksize, 9A)	6SL3000-2BE21-0AA0	REACTOR	---	x	---	x
Motor Reactor (Booksize, 60A)	6SL3000-2BE26-0AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 380-480V, 210A)	6SL3000-2BE32-1AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 380-480V, 260A)	6SL3000-2BE32-6AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 380-480V, 310A)	6SL3000-2BE33-2AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 380-480V, 380A)	6SL3000-2BE33-8AA0	REACTOR	---	x	---	x
Motor Reactor (3AC, 380-480V, 490A)	6SL3000-2BE35-0AA0	REACTOR	---	x	---	x
Motor Reactor (FSA, 3AC, 380-480V, 6.1A)	6SL3202-0AE16-1CA0	REACTOR	---	x	---	x
Motor Reactor (FSA, 3AC, 380-480V, 9.0A)	6SL3202-0AE18-8CA0	REACTOR	---	x	---	x
Motor Reactor (FSB, 3AC, 380-480V, 18.5A)	6SL3202-0AE21-8CA0	REACTOR	---	x	---	x
Motor Reactor (FSC, 3AC, 380-480V, 39A)	6SL3202-0AE23-8CA0	REACTOR	---	x	---	x
Motor Reactor (FSC, 3AC, 200-600V, 35A)	6SL3202-0AJ23-2CA0	REACTOR	---	x	---	x
Braking Resistors						
Braking Resistor (DC, 620V, 20kW, 20Ohm)	6SE7023-2ES87-2DC0	RESISTOR	---	x	---	x
Braking Resistor (DC, 620V, 50kW, 80Ohm)	6SE7028-0ES87-2DC0	RESISTOR	---	x	---	x
Braking Resistor (DC, 600V, 125kW, 4.4Ohm)	6SL3000-1BE31-3AA0	RESISTOR	---	x	---	x
Braking Resistor (DC, 600V, 250kW, 2.2Ohm)	6SL3000-1BE32-5AA0	RESISTOR	---	x	---	x
Braking Resistor (3AC, 380-480V, 500kW)	6SL3000-1BE35-0AA0	RESISTOR	---	x	---	x
Braking Resistor (3AC, 380-480V, 1000kW)	6SL3000-1BE41-0AA0	RESISTOR	---	x	---	x
Braking Resistor (DC, 860V, 125kW, 8.6Ohm)	6SL3000-1BF31-3AA0	RESISTOR	---	x	---	x
Braking Resistor (DC, 860V, 250kW, 3.4Ohm)	6SL3000-1BF32-5AA0	RESISTOR	---	x	---	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Klaus Helmrich, Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The value in column Electrical Equipment (Safety) marks the year of first placing on the market.

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
Braking Resistor (3AC, 500-600V, 550kW)	6SL3000-1BF35-5AA0	RESISTOR	---	x	---	x
Braking Resistor (3AC, 500-600V, 1100kW)	6SL3000-1BF41-1AA0	RESISTOR	---	x	---	x
Braking Resistor (1035V DC, 125kW, 9.8Ohm)	6SL3000-1BH31-3AA0	RESISTOR	---	x	---	x
Braking Resistor (1035V DC, 250kW, 4.9Ohm)	6SL3000-1BH32-5AA0	RESISTOR	---	x	---	x
Braking Resistor (3AC, 660-690V, 630kW)	6SL3000-1BH36-3AA0	RESISTOR	---	x	---	x
Braking Resistor (3AC, 660-690V, 11200kW)	6SL3000-1BH41-2AA0	RESISTOR	---	x	---	x
HFD Resistor (150Ohm, 800W)	6SL3100-1BE21-3AA0	RESISTOR	---	x	---	x
Pulsed Resistor (DC, 600V, 15.6OHM)	6SL3100-1BE22-5AA0	RESISTOR	---	x	---	x
Braking Resistor (DC, 600V, 1.5/100kW)	6SL3100-1BE31-0AA0	RESISTOR	---	x	---	x
Braking Resistor (180Ohm)	6SL3201-0BE12-0AA0	RESISTOR	---	x	---	x
Braking Resistor (370Ohm)	6SL3201-0BE14-3AA0	RESISTOR	---	x	---	x
Braking Resistor (140Ohm)	6SL3201-0BE21-0AA0	RESISTOR	---	x	---	x
Braking Resistor (75Ohm)	6SL3201-0BE21-8AA0	RESISTOR	---	x	---	x
Braking Resistor (300Ohm)	6SL3201-0BE23-8AA0	RESISTOR	---	x	---	x
Braking Modules						
Braking Module (600V DC, 100kW)	6SL3100-1AE31-0AB1	BRK MODULE	---	x	x	x
Braking Module (600V DC, 125kW, Chassis)	6SL3300-1AE31-3AA0	BRK MODULE	---	x	x	x
Braking Module (600V DC, 250kW, Chassis)	6SL3300-1AE32-5AA0	BRK MODULE	---	x	x	x
Braking Module (600V DC, 250kW, Chassis)	6SL3300-1AE32-5BA0	BRK MODULE	---	x	x	x
Braking Module (900V DC, 100kW, Chassis)	6SL3300-1AF31-3AA0	BRK MODULE	---	x	x	x
Braking Module (860V DC, 250kW, Chassis)	6SL3300-1AF32-5AA0	BRK MODULE	---	x	x	x
Braking Module (860V DC, 250kW, Chassis)	6SL3300-1AF32-5BA0	BRK MODULE	---	x	x	x
Braking Module (1035V DC, 125kW, Chassis)	6SL3300-1AH31-3AA0	BRK MODULE	---	x	x	x
Braking Module (1035V DC, 250kW, Chassis)	6SL3300-1AH32-5AA0	BRK MODULE	---	x	x	x
Braking Module (1035V DC, 250kW, Chassis)	6SL3300-1AH32-5BA0	BRK MODULE	---	x	x	x
Braking Module (600V DC, 100kW, Compact)	6SL3400-1AE31-0AA1	BRK MODULE	---	x	x	x
Capacitor Modules						
Capacitor Module (DC, 600V, 4000uF)	6SL3100-1CE14-0AA0	CAP MODULE	---	x	---	x
Control Supply Modules						
Control Supply Module (DC, 26V)	6SL3100-1DE22-0AA1	SUPPLY MODULE	---	x	x	x
Sensor Modules						
VSM 10	6SL3053-0AA00-3AA1	SENSOR MODULE	---	x	x	x
Terminal Modules						
TB30	6SL3055-0AA00-2TA0	TERMINAL MODULE	---	---	x	x
TM31	6SL3055-0AA00-3AA1	TERMINAL MODULE	---	---	x	x
TM54F	6SL3055-0AA00-3BA0	TERMINAL MODULE	x	---	x	x
TM15	6SL3055-0AA00-3FA0	TERMINAL MODULE	---	---	x	x
TM120	6SL3055-0AA00-3KA0	TERMINAL MODULE	---	---	x	x
TM150	6SL3055-0AA00-3LA0	TERMINAL MODULE	---	---	x	x
TM41	6SL3055-0AA00-3PA1	TERMINAL MODULE	---	---	x	x
G120X IO Extension Module	6SL3255-0BE00-0AA0	TERMINAL MODULE	---	---	x	x

The value in column Electrical Equipment (Safety) marks the year of first placing on the market.

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
Communication Modules						
CBC10 (CAN)	6SL3055-0AA00-2CA0	CONTROLLER	---	---	x	x
CBE20 (PN)	6SL3055-0AA00-2EB0	CONTROLLER	---	---	x	x
DMC20	6SL3055-0AA00-6AA1	CONTROLLER	---	---	x	x
DME20 (IP67)	6SL3055-0AA00-6AB0	CONTROLLER	---	---	x	x
Brake Relays						
Brake Relay	6SL3252-0BB00-0AA0	POWER RELAY	---	x	---	x
Safe Brake Relay	6SL3252-0BB01-0AA0	POWER RELAY	x	---	---	x
Hydraulic Modules						
HLA	6SL3420-2HX00-0AA0	CONTROLLER	x	---	x	x
Sensor Modules (Encoder)						
SME91	1FN1910-0AA20-1AA0	SENSOR MODULE	---	x	x	x
SME91 (PT1000)	1FN1910-0AA20-1AA3	SENSOR MODULE	---	x	x	x
SME92	1FN1910-0AA20-2AA0	SENSOR MODULE	---	x	x	x
SME93	1FN1910-0AA20-3AA0	SENSOR MODULE	---	x	x	x
SME93 (PT1000)	1FN1910-0AA20-3AA3	SENSOR MODULE	---	x	x	x
SME94	1FN1910-0AA20-4AA0	SENSOR MODULE	---	x	x	x
SMC10	6SL3055-0AA00-5AA3	SENSOR MODULE	---	---	x	x
SMC20	6SL3055-0AA00-5BA3	SENSOR MODULE	x	---	x	x
SMC30	6SL3055-0AA00-5CA2	SENSOR MODULE	---	---	x	x
SMC40	6SL3055-0AA00-5DA0	SENSOR MODULE	x	---	x	x
SME20	6SL3055-0AA00-5EA3	SENSOR MODULE	x	---	x	x
SME25	6SL3055-0AA00-5HA3	SENSOR MODULE	x	---	x	x
SME120	6SL3055-0AA00-5JA3	SENSOR MODULE	x	---	x	x
SME125	6SL3055-0AA00-5KA3	SENSOR MODULE	x	---	x	x
SMI24	6SL3055-0AA00-5SA3	SENSOR MODULE	x	---	x	x
Operator Panels						
BOP-20	6SL3055-0AA00-4BA0	PANEL	---	---	x	x
AOP30	6SL3055-0AA00-4CA5	PANEL	---	---	x	x
BOP	6SL3255-0AA00-4BA1	PANEL	---	---	x	x
BOP-2	6SL3255-0AA00-4CA1	PANEL	---	---	x	x
IOP (hand held kit)	6SL3255-0AA00-4HA0	PANEL	---	---	x	x
IOP (hand held kit 2)	6SL3255-0AA00-4HA1	PANEL	---	---	x	x
IOP	6SL3255-0AA00-4JA1	PANEL	---	---	x	x
IOP-2	6SL3255-0AA00-4JA2	PANEL	---	---	x	x
IOP (Chinese)	6SL3255-0AA00-4JC1	PANEL	---	---	x	x
Memory						
Compactflash (S120, V 4.7)	6SL3054-0EH00-1BA0	MEMORY	---	---	x	x
Compactflash (S120, V 4.7 perf.)	6SL3054-0EH01-1BA0	MEMORY	---	---	x	x
Compactflash (S120, V 4.8)	6SL3054-0EJ00-1BA0	MEMORY	---	---	x	x
Compactflash (S120, V 4.8 perf.)	6SL3054-0EJ01-1BA0	MEMORY	---	---	x	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Klaus Helmrich, Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The value in column Electrical Equipment (Safety) marks the year of first placing on the market.

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
Compactflash (S120, V 5.1)	6SL3054-0FB00-1BA0	MEMORY	---	---	x	x
Compactflash (S120, V 5.1 perf.)	6SL3054-0FB01-1BA0	MEMORY	---	---	x	x
Compactflash (S120, V 5.1 SP1)	6SL3054-0FB10-1BA0	MEMORY	---	---	x	x
Compactflash (S120, V 5.1 SP1 perf.)	6SL3054-0FB11-1BA0	MEMORY	---	---	x	x
Compactflash (S120, V 5.1 HF1)	6SL3054-0FC00-1BA0	MEMORY	---	---	x	x
Compactflash (S120, V 5.1 HF1 perf.)	6SL3054-0FC01-1BA0	MEMORY	---	---	x	x
Compactflash (G150, V 5.2)	6SL3054-1FC00-1BA0	MEMORY	---	---	x	x
Compactflash (S150, V 5.2)	6SL3054-2FC00-1BA0	MEMORY	---	---	x	x
Compactflash (G130, V 5.2)	6SL3054-3FC00-1BA0	MEMORY	---	---	x	x
MMC (64MB)	6SL3054-4AG00-0AA0	MEMORY	---	---	x	x
SD-Card (G120, 512MB)	6SL3054-4AG00-2AA0	MEMORY	---	---	x	x
SD-Card (S210, V 5.1 SP1)	6SL3054-4FB10-2BA0	MEMORY	---	---	x	x
SD-Card (S210, V 5.2)	6SL3054-4FC00-2BA0	MEMORY	---	---	x	x
SD-Card (G120, FW 4.7)	6SL3054-7EH00-2BA0	MEMORY	---	---	x	x
SD-Card (G120, FW 4.7)	6SL3054-7TF00-2BA0	MEMORY	---	---	x	x
Encoder						
Encoder (TTL, inc, RS422)	6FX2001-2CA50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2CB00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2CB02	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2CB25	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2CB50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2CC00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2CC04	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2CC50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2CD60	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2CF00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2DA50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2DB00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2DB02	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2DB25	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2DB50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2DC00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2DC04	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2DC50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2DD60	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2DF00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2EA50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2EB00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2EB02	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2EB25	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2EB50	SENSOR	---	---	x	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Klaus Helmrich, Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The value in column Electrical Equipment (Safety) marks the year of first placing on the market.

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
Encoder (TTL, inc, RS422)	6FX2001-2EC00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2EC04	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2EC50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2ED60	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2EF00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2FA50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2FB00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2FB02	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2FB25	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2FB50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2FC00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2FC04	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2FC50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2FD60	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2FF00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2GA50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2GB00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2GB02	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2GB25	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2GB50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2GC00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2GC04	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2GC50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2GD60	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2GF00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2HA50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2HB00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2HB02	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2HB25	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2HB50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2HC00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2HC04	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2HC50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2HD60	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2HF00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2MA50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2MB00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2MB02	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2MB25	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2MB50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2MC00	SENSOR	---	---	x	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Klaus Helmrich, Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The value in column Electrical Equipment (Safety) marks the year of first placing on the market.

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
Encoder (TTL, inc, RS422)	6FX2001-2MC04	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2MC50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2MD60	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2MF00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2NA50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2NB00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2NB02	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2NB25	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2NB50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2NC00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2NC04	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2NC50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2ND60	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2NF00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2PA50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2PB00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2PB02	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2PB25	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2PB50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2PC00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2PC04	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2PC50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2PD60	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2PF00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2QA50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2QB00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2QB02	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2QB25	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2QB50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2QC00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2QC04	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2QC50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2QD60	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2QF00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2RA50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2RB00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2RB02	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2RB25	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2RB50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2RC00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2RC04	SENSOR	---	---	x	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Klaus Helmrich, Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The value in column Electrical Equipment (Safety) marks the year of first placing on the market.

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
Encoder (TTL, inc, RS422)	6FX2001-2RC50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2RD60	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2RF00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2SA50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2SB00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2SB02	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2SB25	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2SB50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2SC00	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2SC04	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2SC50	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2SD60	SENSOR	---	---	x	x
Encoder (TTL, inc, RS422)	6FX2001-2SF00	SENSOR	---	---	x	x
Encoder (sin/cos, inc, 1Vpp)	6FX2001-3CB00	SENSOR	---	---	x	x
Encoder (sin/cos, inc, 1Vpp)	6FX2001-3CB02	SENSOR	---	---	x	x
Encoder (sin/cos, inc, 1Vpp)	6FX2001-3CC50	SENSOR	---	---	x	x
Encoder (sin/cos, inc, 1Vpp)	6FX2001-3EB00	SENSOR	---	---	x	x
Encoder (sin/cos, inc, 1Vpp)	6FX2001-3EB02	SENSOR	---	---	x	x
Encoder (sin/cos, inc, 1Vpp)	6FX2001-3EC50	SENSOR	---	---	x	x
Encoder (sin/cos, inc, 1Vpp)	6FX2001-3GB00	SENSOR	---	---	x	x
Encoder (sin/cos, inc, 1Vpp)	6FX2001-3GB02	SENSOR	---	---	x	x
Encoder (sin/cos, inc, 1Vpp)	6FX2001-3GC50	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4DA10	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4DA50	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4DB00	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4DC50	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4FA10	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4FA50	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4FB00	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4FC50	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4HA10	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4HA50	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4HB00	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4HC50	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4NA10	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4NA50	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4NB00	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4NC50	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4QA10	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4QA50	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4QB00	SENSOR	---	---	x	x

Siemens Aktiengesellschaft: Chairman of the Supervisory Board: Jim Hagemann Snaube; Managing Board: Roland Busch, Chairman, President and Chief Executive Officer; Klaus Helmrich, Cedrik Neike, Matthias Rebellius, Ralf P. Thomas, Judith Wiese; Registered offices: Berlin and Munich, Germany; Commercial registries: Berlin-Charlottenburg, HRB 12300, Munich, HRB 6684; WEEE-Reg.-No. DE 23691322

The value in column Electrical Equipment (Safety) marks the year of first placing on the market.

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
Encoder (HTL, inc)	6FX2001-4QC50	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4SA10	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4SA50	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4SB00	SENSOR	---	---	x	x
Encoder (HTL, inc)	6FX2001-4SC50	SENSOR	---	---	x	x
Encoder (DQ, abs, ST, 22 Bit)	6FX2001-5FD13-0AA1	SENSOR	---	---	x	x
Encoder (G95, abs, ST, 24 Bit)	6FX2001-5FD13-1AA0	SENSOR	---	---	x	x
Encoder (DQ, abs, MT, 34 Bit)	6FX2001-5FD25-0AA1	SENSOR	---	---	x	x
Encoder (G95, abs, MT, 36 Bit)	6FX2001-5FD25-1AA0	SENSOR	---	---	x	x
Encoder (EnDat, abs, ST, 13 Bit)	6FX2001-5FE13	SENSOR	---	---	x	x
Encoder (EnDat, abs, MT, 25 Bit)	6FX2001-5FE25	SENSOR	---	---	x	x
Encoder (PN, abs, ST, 13 Bit)	6FX2001-5FN13	SENSOR	---	---	x	x
Encoder (PN, abs, MT, 27 Bit)	6FX2001-5FN25	SENSOR	---	---	x	x
Encoder (DP, abs, ST, 13 Bit)	6FX2001-5FP12	SENSOR	---	---	x	x
Encoder (DP, abs, MT, 27 Bit)	6FX2001-5FP24	SENSOR	---	---	x	x
Encoder (SSI, abs, ST, 13 Bit)	6FX2001-5FS12	SENSOR	---	---	x	x
Encoder (SSI, abs, MT, 25 Bit)	6FX2001-5FS24	SENSOR	---	---	x	x
Encoder (EnDat, abs, ST, 13 Bit)	6FX2001-5HE13	SENSOR	---	---	x	x
Encoder (EnDat, abs, MT, 25 Bit)	6FX2001-5HE25	SENSOR	---	---	x	x
Encoder (SSI, abs, ST, 13 Bit)	6FX2001-5HS12	SENSOR	---	---	x	x
Encoder (SSI, abs, MT, 25 Bit)	6FX2001-5HS24	SENSOR	---	---	x	x
Encoder (DQ, abs, ST, 22 Bit)	6FX2001-5QD13-0AA1	SENSOR	---	---	x	x
Encoder (G95, abs, ST, 24 Bit)	6FX2001-5QD13-1AA0	SENSOR	---	---	x	x
Encoder (DQ, abs, MT, 34 Bit)	6FX2001-5QD25-0AA1	SENSOR	---	---	x	x
Encoder (G95, abs, MT, 36 Bit)	6FX2001-5QD25-1AA0	SENSOR	---	---	x	x
Encoder (EnDat, abs, ST, 13 Bit)	6FX2001-5QE13	SENSOR	---	---	x	x
Encoder (EnDat, abs, MT, 25 Bit)	6FX2001-5QE25	SENSOR	---	---	x	x
Encoder (PN, abs, ST, 13 Bit)	6FX2001-5QN13	SENSOR	---	---	x	x
Encoder (PN, abs, MT, 27 Bit)	6FX2001-5QN25	SENSOR	---	---	x	x
Encoder (DP, abs, ST, 13 Bit)	6FX2001-5QP12	SENSOR	---	---	x	x
Encoder (DP, abs, MT, 27 Bit)	6FX2001-5QP24	SENSOR	---	---	x	x
Encoder (SSI, abs, ST, 13 Bit)	6FX2001-5QS12	SENSOR	---	---	x	x
Encoder (SSI, abs, MT, 25 Bit)	6FX2001-5QS24	SENSOR	---	---	x	x
Encoder (EnDat, abs, ST, 13 Bit)	6FX2001-5SE13	SENSOR	---	---	x	x
Encoder (EnDat, abs, MT, 25 Bit)	6FX2001-5SE25	SENSOR	---	---	x	x
Encoder (SSI, abs, ST, 13 Bit)	6FX2001-5SS12	SENSOR	---	---	x	x
Encoder (SSI, abs, MT, 25 Bit)	6FX2001-5SS24	SENSOR	---	---	x	x
Encoder (DQ, abs, ST, 22 Bit)	6FX2001-5VD13-0AA1	SENSOR	---	---	x	x
Encoder (G95, abs, ST, 24 Bit)	6FX2001-5VD13-1AA0	SENSOR	---	---	x	x
Encoder (DQ, abs, MT, 34 Bit)	6FX2001-5VD25-0AA1	SENSOR	---	---	x	x
Encoder (G95, abs, MT, 36 Bit)	6FX2001-5VD25-1AA0	SENSOR	---	---	x	x

The value in column Electrical Equipment (Safety) marks the year of first placing on the market.

Product	MLFB	Description	Supply of Machinery (Safety)	Electrical Equipment (Safety)	Electromagnetic Compatibility	RoHS
Encoder (DQ, abs, ST, 22 Bit)	6FX2001-5WD13-0AA1	SENSOR	---	---	x	x
Encoder (G95, abs, ST, 24 Bit)	6FX2001-5WD13-1AA0	SENSOR	---	---	x	x
Encoder (DQ, abs, MT, 34 Bit)	6FX2001-5WD25-0AA1	SENSOR	---	---	x	x
Encoder (G95, abs, MT, 36 Bit)	6FX2001-5WD25-1AA0	SENSOR	---	---	x	x
Encoder (PN, abs, ST, 13 Bit)	6FX2001-5WN13	SENSOR	---	---	x	x
Encoder (PN, abs, MT, 27 Bit)	6FX2001-5WN25	SENSOR	---	---	x	x
Encoder (DP, abs, ST, 13 Bit)	6FX2001-5WP12	SENSOR	---	---	x	x
Encoder (DP, abs, MT, 27 Bit)	6FX2001-5WP24	SENSOR	---	---	x	x
Housing						
SINAMICS Bus Adapter (DC, 24V)	6SL3162-2AA00-0AA0	ADAPTER KIT	---	---	---	x
SINAMICS Terminal Supply Adapter	6SL3162-2BD00-0AA0	PWR ADAPTER	---	x	---	x
SINAMICS Terminal Supply Adapter	6SL3162-2BE00-0AA0	PWR ADAPTER	---	x	---	x
SINAMICS Terminal Supply Adapter	6SL3162-2BM00-0AA0	PWR ADAPTER	---	x	---	x
DC Link Adapter (35-95mm ²)	6SL3162-2BM01-0AA0	PWR ADAPTER	---	x	---	x
DC Link Adapter (35-95mm ²)	6SL3162-2BM10-0AA0	PWR ADAPTER	---	x	---	x
DC Bridge (50mm)	6SL3162-2BM20-0AA0	PWR ADAPTER	---	x	---	x
S120 Motor Connector (3-30A)	6SL3162-2MA00-0AA0	PWR ADAPTER	---	x	---	x
S120 Motor Connector (3-30A)	6SL3162-2MA00-0AC0	PWR ADAPTER	---	x	---	x
S120 Motor Connector (X1)	6SL3162-2MA00-0AX0	PWR ADAPTER	---	x	---	x
S120 Motor Connector Compact (X1)	6SL3162-2MA01-0AX0	PWR ADAPTER	---	x	---	x
Motor Connector (Push-In, 3-30A)	6SL3162-2MB00-0AC0	PWR ADAPTER	---	x	---	x
Motor Connector (Push-In, 3-30A, 10mm ²)	6SL3162-2MC00-0AC0	PWR ADAPTER	---	x	---	x
Motor Adapter (C-/D-Type 2.5mm ²)	6SL3162-2ME01-0AC0	PWR ADAPTER	---	x	---	x
Motor Adapter (C-/D-Type 6mm ²)	6SL3162-2ME02-0AC0	PWR ADAPTER	---	x	---	x
PC-Inverter Connection Kit	6SL3255-0AA00-2AA1	ADAPTER KIT	---	---	---	x
PC-Inverter Connection Kit	6SL3255-0AA00-2CA0	ADAPTER KIT	---	---	---	x
SINAMICS Connect	6SL3255-0AG30-0AA0	OPTION MODULE	---	---	x	x
G120X FSG Terminal Supply Adapter	6SL3266-2HG00-0BA0	PWR ADAPTER	---	x	---	x
AIM Internal Fan Unit	6SL3358-0AJ04-0FA0	SPARE PART	---	x	x	x
Chassis Internal Fan Unit	6SL3358-0BF04-0FA0	SPARE PART	---	x	x	x