

Industrial Identification Systems

SIMATIC Ident



siemens.com/ident

Related catalogs

Industrial Communication SIMATIC NET	IK PI		Weighing TechnologyWT 10Products for Weighing Technology	
E86060-K6710-A101-B8-7600			E86060-K6410-A101-A4-7600	die Wigetechnik
SIMATIC Products for Totally Integrated Automation	ST 70	Products for Danily	SIMATIC HMI / ST 80/ST PC PC-based Automation Human Machine Interface Systems PC-based Automation	EXERCISE FOR A SUBJECT OF A SU
E86060-K4670-A101-B5-7600			E86060-K4680-A101-C2-7600	
SITOP Power supply SITOP	KT 10.1		SITRAIN ITC Training for Industry	EVELS
E86060-K2410-A101-B1-7600		ATTOR	Only available in German E86060-K6850-A101-C5	STRAIN - Training for Industry
Industrial Controls SIRIUS	IC 10		Products for Automation and Drives CA 01 Interactive Catalog, DVD	SIMIN
PDF (E86060-K1010-A101-A6-7600)		Industrial Controls	E86060-D4001-A510-D6-7600	
Safety Integrated Safety Technology for Factory Automation	SI 10	LOUX	Industry Mall Information and Ordering Platform in the Internet:	
E86060-K7010-A101-A3-7600		Are Factory Automation	www.siemens.com/industrymall	
Process Automation Field Instruments for Process Automation	FI 01			
PDF (E86060-K6201-A101-B9-7600)		Process Automation		

Industrial Identification Systems

SIMATIC Ident



Catalog ID 10 · 2016

Supersedes: Catalog ID 10 · 2014

Refer to the Industry Mall for current updates of this catalog: www.siemens.com/industrymall

The products contained in this catalog can also be found in the Interactive Catalog CA 01. Article No.: E86060-D4001-A510-D6-7600

Please contact your local Siemens branch.

© Siemens AG 2016

SIMATIC Ident SIMATIC Ident - for more economic production and logistics processes Simple integration into the automation level Digital Enterprise RFID systems field data table	1
RFID systems for the HF range Transponders SIMATIC RF200 SIMATIC RF300 MOBY D Antennas	2
RFID system for the UHF range SIMATIC RF600 Transponders Readers Antennas	3
Optical identification Stationary code reading systems Handheld reading systems Verification systems Optical character recognition (OCR) Object recognition	4
Communication modules for RFID systems and optical identification RFID standard cables SCALANCE network components	5
Appendix	6



The products and systems described in this catalog are manufactured/distributed under application of a certified quality management system in accordance with DIN EN ISO 9001. The certificate is recognized by all IQNet countries.



Answers for industry.

Integrated technologies, vertical market expertise and services for greater productivity, energy efficiency, and flexibility.

Siemens is the world's leading supplier of innovative and environmentally friendly products and solutions for industrial companies. End-to-end automation technology and industrial software, solid market expertise, and technology-based services are the levers we use to increase our customers' productivity, efficiency and flexibility. We consistently rely on integrated technologies and, thanks to our bundled portfolio, we can respond more quickly and flexibly to our customers' wishes. With our globally unmatched range of automation technology, industrial control and drive technology as well as industrial software, we equip companies with exactly what they need over their entire value chain – from product design and development to production, sales and service. Our industrial customers benefit from our comprehensive portfolio, which is tailored to their market and their needs. Market launch times can be reduced by up to 50% due to the combination of powerful automation technology and industrial software. At the same time, the costs for energy or waste water for a manufacturing company can be reduced significantly. In this way, we increase our customers' competitive strength and make an important contribution to environmental protection with our energy-efficient products and solutions.





Efficient automation starts with efficient engineering.

Totally Integrated Automation: Efficiency driving productivity.

Efficient engineering is the first step toward better production that is faster, more flexible, and more intelligent. With all components interacting efficiently, Totally Integrated Automation (TIA) delivers enormous time savings right from the engineering phase. The result is lower costs, faster time-to-market, and greater flexibility.





PROFINET

PROFIBUIS

AS-Interface

Totally Integrated

Power

Industrial Ethernet

KNX GAMMA instabus



A unique complete approach for all industries

As one of the world's leading automation suppliers, Siemens provides an integrated, comprehensive portfolio for all requirements in process and manufacturing industries. All components are mutually compatible and system-tested. This ensures that they reliably perform their tasks in industrial use and interact efficiently, and that each automation solution can be implemented with little time and effort based on standard products. The integration of many separate individual engineering tasks into a single engineering environment, for example, provides enormous time and cost savings.

With its comprehensive technology and industry-specific expertise, Siemens is continuously driving progress in manufacturing industries – and Totally Integrated Automation plays a key role.

Totally Integrated Automation creates real value added in all automation tasks, especially for:

Integrated engineering

Consistent, comprehensive engineering throughout the entire product development and production process

- Industrial data management Access to all important data occurring in productive operation – along the entire value chain and across
- all levels
 Industrial communication
 Integrated communication based on international
- cross-vendor standards that are mutually compatible Industrial security
- Systematic minimization of the risk of an internal or external attack on plants and networks
- Safety Integrated
- Reliable protection of personnel, machinery, and the environment thanks to seamless integration of safety technologies into the standard automation

Making things right with Totally Integrated Automation

Totally Integrated Automation, industrial automation from Siemens, stands for the efficient interoperability of all automation components. The open system architecture covers the entire production process and is based on end-to-end shared characteristics: consistent data management, global standards, and uniform hardware and software interfaces.

Totally Integrated Automation lays the foundation for comprehensive optimization of the production process:

- Time and cost savings due to efficient engineering
- Minimized downtime due to integrated diagnostic functions
- Simplified implementation of automation solutions due to global standards
- Better performance due to interoperability of systemtested components

© Siemens AG 2016

© Siemens AG 2016

SIMATIC Ident



1/2	SIMATIC Ident - for more economic production and logistics processes
1/4	Production Control
1/4	Asset Management
1/5	Tracking and Tracing
1/5	Supply Chain Management
1/6	Simple integration into the automation level
1/6	Simple integration into the automation level Digital Enterprise

Siemens ID 10 · 2016

To be able to stay ahead in dynamic markets in the face of increasing competition, stricter standards and statutory obligations, shorter product life cycles, more individual customer requirements, and increasingly globalized value-added, companies must be in a position to significantly boost the efficiency of their value added chains. in production control, asset management, tracking & tracing as well as in supply chain management. By using innovative identification technologies, companies can gain an important advantage. In connection with high-performance, reliable communication networks, this creates the infrastructure that prepares companies for the forthcoming industrial digitization.

We offer SIMATIC Ident, a unique portfolio for industrial identification which can provide the perfect solution for your requirements while keeping you flexible for the future.

The right identification technology depends on factors such as sensing distance, lighting conditions, single or repeat markings, as well as environmental effects such as temperature and pollution.

Whether RFID, barcode, DMC or OCR: every technology has its specific strengths. Optical character recognition is used for cases in which codes must also be readable for persons, such as use-by dates.

2D codes and RFID impress customers with their high level of data security and have proved reliable even under harsh industrial conditions.

The decisive criterion for an identification system: Your individual application.

SIMATIC Ident

SIMATIC Ident - for more economic production and logistics processes



RFID is the ideal solution when there is no line of sight between the reader and the marking, large volumes of data or wide ranges are required, or the stored information has to be changed. Here the product or object is fitted with a memory chip that can be programmed and read using radio techniques. With low-cost SmartLabels available for logistics, rugged data memories for assembly lines as well as transponders with a wide range, RFID is perfectly suited to a variety of different applications.

Our intelligent SIMATIC RF system family offers you transparency without gaps. Data is therefore available at any time along the complete production and distribution chain - for perfect control and optimization of material flow and logistics. Identification, verification: Optical identification



When higher performance is required, 2D codes are recommended as an alternative to barcodes. 2D codes offer more memory capacity, higher reading rates, and enhanced reading security. They can be applied inexpensively, e.g. together with shipping labels. They also enable products to be marked directly (Direct Part Marking, DPM) using lasers, printing or dot-peening, which is extremely resistant to external influences. 2D codes can be read with complete reliability even from a small viewing angle or under difficult lighting conditions.

With our optical reading devices, we offer you the ideal solution for reading and verifying 1D and 2D codes as well as for text recognition (OCR) and object recognition (Pat-Genius) for the reliable tracing of production batches beyond the manufacturing plant.

SIMATIC Ident

SIMATIC Ident - for more economic production and logistics processes



Example configuration of a small assembly line with SIMATIC RF200

All over the world, consumers want more and more individual products. Versatile production and material flow control with industrial identification handles the requirements for growing product variety throughout the manufacturing process. This is made possible by reliable, efficient and cost-effective maketo-order production.



Asset Management



Example configuration of a small assembly line with SIMATIC RF600, SCALANCE W and SCALANCE X

Assets such as tools, plant parts, or containers are essential for production and logistics. Industrial identification ensures they are used efficiently. The inventory can be acquired in real time and the status determined precisely. This means that the use of the assets can be monitored perfectly at any time and optimized specifically for stock quantity, capacity and maintenance.



SIMATIC Ident - for more economic production and logistics processes

Tracking & Tracing

With industrial identification, each product leaves a digital trail that can be seamlessly traced and documented back to the origin of its individual components. This permits full transparency of the entire product life cycle and therefore the best possible quality.



Example configuration of tracking & tracing with optical reading devices

Supply Chain Management

Competitive production on an industrial scale requires global supply chains for individual parts and components. Industrial identification makes these supply chains transparent and predictable, and facilitate optimum planning. This avoids delivery bottlenecks and downtimes, optimizes warehouse stocks and improves profit margins.



Example configuration of a logistics portal with SIMATIC RF600 and SCALANCE W

SIMATIC Ident

Simple integration into the automation level

With our SIMATIC Ident portfolio we can offer you the right solution: Using communication modules and convenient function blocks, it is easy to connect SIMATIC Ident systems to the PLC (such as SIMATIC) or the IT landscape. This ensures that you have a system-wide, uniform software architecture and saves considerable outlay and costs in engineering, commissioning and maintenance.



Integration in Totally Integrated Automation



Connection to third-party systems

Digital Enterprise



The Internet serves as an enormous accelerator of business processes and has revolutionized business operations around the world Not only does it enable enterprises to work more closely and effectively with their business partners, it also puts them in a position to communicate directly with end customers and respond very quickly to specific requests (mass customization). The resulting requirements present the industry and the products and services it provides with new challenges never seen before.

Manufacturing companies are being forced to drastically shorten throughput times with massively improved flexibility in order to keep up with the increasingly strong trend toward individualized mass production. At the same time, they must consistently reducing their consumption of energy and raw materials. Solutions to address these challenges are being developed in initiatives such as the "Internet of Things" or "Industrie 4.0".

The requirements listed above which arise from the tremendous pace at which the internet economy is developing can no longer be met just by focusing on automation processes in the manufacturing industry. What is required is a holistic approach stretching over the entire value-add chain, starting with the product definition and extending to service and maintenance of the product in everyday use. Special attention must be paid here to a deep level of integration and seamless connection of data with the supplier network



Essential components for the digital infrastructure are powerful communication networks and reliable, automatic synchronization of digital processes with workflows in the real world. Siemens offers a unique portfolio to deal with both of these aspects: SIMATIC NET for high-performance networks, and SIMATIC Ident for industrial identification with RFID or optical identification. In addition to integrating manufacturers and suppliers in a comprehensive production network, demands with regard to asset management, supply chain management or Tracking & Tracing can also be effectively solved at low cost.

Explanation of symbols appearing below product images

"Highlight" symbols can be found under most product pictures. These symbols refer to the outstanding properties of the particular product. The following table describes the meaning of the symbols.

Symbol	Meaning	P
-25 / 100 °C	Device capable of operating in wide temperature range (with specification of range).	
•••	Wide operating distance between transponder and	-
←	reader possible (with specification of max. distance).	E
200 mm		_
	The transponder can be mounted directly onto metal surfaces.	_
METAL	The transmonday as used as is some still a with the ICO	
ISO	protocol.	
RF300	The transponder is compatible with the RF300 protocol.	
	The transponder or reader has ATEX approval	
	(with specification of approval).	ĺ
ATEX II 2D	The transponder or antenna is small in design	-
small	The transponder of antenna is small in design.	
* /	The antenna is large in design. This enable a large	-
	transmission window.	
✓ big ↘		p
)))	The reader has a high data transfer rate for wireless transmission.	
106 kbit/s		
	The transponder or reader has a high processing speed.	
Speed		
	The transponder has a large user memory (with specification of storage capacity).	
8 Kbyte		S
•• • R\$232	The reader has an RS232 interface for connection to SIMATIC, PC-based systems or third-party controllers.	
	The reader can be connected to SIMATIC S7_PROFIBUS	-
	PROFINET, Ethernet/IP or Ethernet TCP/IP via communication modules.	
CM	The reader has an IO Link interface for according to	1
ð IO- Link	ID-Link master modules from Siemens or third-party manufacturers.	,
	The communication module has a PROFIBUS	
PROFII [®] BUS	connection.	ĺ
		F

Symbol	Meaning								
<u>prof</u> i Net o	The communication module has a PROFINET connection.								
PROF NET	The reader has PROFINET and Ethernet TCP/IP for connecting SIMATIC, SIMOTION, SINUMERIK, PC-based systems and third-party controllers.								
Industrial	The communication module has an Ethernet connection.								
EtherNet/IP	The communication module has an Ethernet/IP connection.								
ET 200pro	The communication module connects SIMATIC Ident systems to the ET 200pro distributed I/O system.								
S7-300	The communication module connects SIMATIC Ident systems to SIMATIC ET200 M and SIMATIC S7-300								
S7-1200	The communication module connects SIMATIC Ident systems to SIMATIC S7-1200.								
WBM	Web Based Management (WBM): The code reader has an onboard web server and can be configured using a multitude of devices that have browser functionality.								
scalable	The functionality of the optical reader is, to a large extent, able to be scaled to different sizes and performance classes with the same user interface and an almost identical electrical interface.								
programmable	The optical reader functions can be dynamically configured using the user interface.								
Linear	The antenna has linear polarization.								
Circular	The antenna has circular polarization.								
10100100101 01100101001 100101 Scanmode	Reader available in Scanmode variant (read-only). In these variants, the reader reads each detected transponder automatically and outputs this data via the serial interface.								
	The optical handheld reader has a USB interface.								
Wireless	The optical handheld reader is suitable for wireless communication.								
	The optical handheld reader is equipped with integrated bright field/dark field lighting.								
Light RS422/232	The device has an RS422 and RS232 interface for connecting readers, optical handheld devices and other serial devices.								

Frequency range	HF			UHF		
RFID system	SIMATIC RF200	SIMATIC RF300	MOBY D	SIMATIC RF600		
		EXERCISE EXE				
Transmission frequency	13.56 MHz	13.56 MHz	13.56 MHz	865 868 MHz (ETSI)		
				902 928 MHz (FCC)		
				920 925 MHz (CMIIT)		
Range, max.	650 mm	210 mm	380 mm	8 m		
Protocol (air interface)	• ISO 15693	• ISO 15693	• ISO 15693	• EPCglobal Class 1 Gen 2,		
	• ISO 18000-3	• ISO 18000-3	• ISO 18000-3	• ISO 18000-6B		
		RF300 (proprietary)		• ISO 18000-6C		
Standards, specifications,	• EN 300330, 301489, CE	• EN 300330, 301489, CE	• EN 300330, 301489, CE	• ETSI EN 302208, CE		
approvals ¹⁾	• FCC Part 15	• FCC Part 15	FCC Part 15	• FCC		
	• UL/CSA	• UL/CSA	• UL/CSA	• UL		
		• ATEX				
Memory capacity, max.	992 bytes (EEPROM)/	64 KB	992 bytes (EEPROM)/	496 bit EPC		
	8 192 bytes (FRAM)		2 000 bytes (FRAM)	3 424 byte		
Maximum data transfer rate for wireless transmission	26.5 Kbps	106 Kbps	26.5 Kbps	300 Kbps		
Multitag/Bulk capability	With RF290R reader only	No	Yes	Yes		
Special features	Particularly compact designs	High data transfer rate	SIMATIC or PC/IT integration	SIMATIC or PC/IT integration		
	For particularly low-cost RFID solutions	• Extended diagnostic possibilities	External antennas for industrial applications	 Data preprocessing in the readers 		
	 IO-Link for simple identification tasks 	High memory capacity		 Special antennas for industrial applications 		

Technical specifications

The following field data table provides a brief summary of all permissible combinations of readers and transponders as well as the most important technical features of the transponders.

This field data table helps by providing an overview of the many different possible combinations of our RFID products.

¹⁾ All current approvals can be found on the Internet at: http://www.siemens.com/rfid-approvals

SIMATIC Ident RFID systems field data table

1

SIMATIC Ident

Overview

RFID systems field data table

1

HF range (RF200, RF300, MOBY D)

5 (,	· · ·																			
Operating distance T (mm) between trans- ponder and reader	ransponder Article No.	MDS D165 6GT2600– 1AB00–0AX0	MDS D261 6GT2600- 1AA01-0AX0	MDS D100 6GT2600– 0AD10	MDS D200 6GT2600- 1AD00-0AX0	MDS D400 6GT2600- 4AD00	MDS D421 6GT2600– 4AE00	MDS D521 6GT2600– 5AE00	MDS D422 6GT2600- 4AF00	MDS D522 6GT2600- 5AF00	MDS D522 6GT2600- 5AF00-0AX0	MDS D423 6GT2600– 4AA00	MDS D124 6GT2600- 0AC10	MDS D324 6GT2600– 3AC00	MDS D424 6GT2600- 4AC00	MDS D524 6GT2600- 5AC00	MDS D425 6GT2600- 4AG00	MDS D525 6GT2600– 5AG00	MDS D126 6GT2600- 0AE00	
					SERVER SPECIFIC AND	SENSES VECTOR annualment	SIEMENS MDS D421 A	SIEMENS NOS OS21 A		STEMENS (KODOO SATO) MGAN (A)		•				$\overline{\mathbf{\cdot}}$	SIEMENS ED/2000-44-00 MGC DQS	SIEMENS ETYMO-6.vx0 VGS 0.25 XS 4.	SIEMENS GOTIZODO AREADO MOS D128 MOSY D 41.4	
User memory		112 byte	256 byte	112 byte	256 byte	2 kbyte	2 kbyte	8 kbyte	2 kbyte	8 kbyte	8 kbyte	2 kbyte	112 byte	992 byte	2 kbyte	8 kbyte	2 kbyte	8 kbyte	112 byte	
Temperature range		–25 °C 85 °C	–25 °C 85 °C	–25 °C 80 °C	–20 °C 60 °C	–20 °C 60 °C	–40 °C 100 °C	–40 °C 100 °C	-40 °C 100 °C	–40 °C 100 °C	–40 °C 100 °C	–40 °C 100 °C	–40 °C 180 °C	–40 °C 140 °C	–40 °C 100 °C	–40 °C 100 °C	–40 °C 125 °C	–40 °C 125 °C	-40 °C 100 °C	
L x W x H or Ø x H (mm)		86 x 54 x 0.3	55 x 55 x 0.3	85.6 x 54 x 0.9	85.6 x 54 x 0.8	85.6 x 54 x 0.8	Ø 10 x 4.5	Ø 10 x 4.5	Ø 20 x 6	Ø 20 x 6	Ø 18 x 5.2	Ø 30 x 8	Ø 27 x 4	Ø 27 x 10	Ø 24 x 10	Ø 50 x 3.6				
	Page	2/8	2/8	2/10	2/12	2/14	2/16	2/18	2/20	2/22	2/22	2/24	2/26	2/28	2/30	2/32	2/34	2/36	2/38	
RF200 reader	2/78			•												•	•			
RF210R	2/79	-	-	-	-	-	0 3	0 3	1 9	18	18	2 10	1 18	1 8	1 16	1 15	1 6	-	-	
RF220R	2/83	5 36	5 30	1 35	5 35	-	1 5	1 5	1 12	1 10	1 10	2 24	1 28	2 21	2 25	2 22	1 11	-	2 30	
RF240R	2/86	2 80	2 60	2 84	2 69	2 80	-	-	1 12	1 10	1 10	2 35	2 53	1 36	1 47	1 45	1 15	-	2 57	
RF250R with ANT 3	2/90	-	-	-	-	-	-	-	1 12	1 12	1 12	0 24	2 32	2 32	0 45	1 30	0 16	-	-	
RF250R with ANT 3S	2/90	-	-	-	-	-	0 3	0 3	-	-	-	-	-	-	-	-	-	-	-	
RF250R with ANT 8	2/90	-	-	-	-	-	0 3	0 3	-	-	-	-	-	-	-	1 8	-	-	-	
RF250R with ANT 12	2/90	-	-	-	-	-	0 3	0 3	0 7	1 7	1 7	-	-	1 10	-	1 15	0 8	-	-	
RF250R with ANT 18	2/90	-	-	-	-	-	0 3	0 4	1 8	1 10	1 10	1 15	0 24	1 18	1 27	1 25	1 11	-	-	
RF250R with ANT 30	2/90	1 45	1 40	1 50	1 45	1 42	-	-	0 12	1 12	1 12	0 18	1 35	1 22	0 34	1 35	1 12	-	0 47	
RF260R	2/95	2 120	2 75	2 110	2 100	2 110	-	-	-	-	-	2 40	2 80	2 60	2 60	2 60	-	-	2 75	
RF290R with ANT D1	2/99	10 180	-	10 180	10 170	10 170	-	-	-	20 25	20 25	10 55	0 100	0 90	0 90	0 90	-	-	5 110	
RF290R with ANT D5	2/99	0 350	0 300	0 400	0 400	0 400	-	-	-	-	-	-	0 200	0 200	0 200	0 200	-	-	0 350	
RF290R with ANT D6	2/99	0 400	0 350	0 550	0 500	0 500	-	-	-	-	-	-	0 220	0 200	0 220	0 220	-	-	0 400	
RF290R with ANT D10	2/99	0 350	0 350	0 500	0 450	0 400	-	-	-	-	-	-	0 200	0 200	0 200	0 220	-	-	0 400	
RF300 reader	2/104																			
RF310R	2/105	2 90	2 74	2 93	2 84	2 104	-	-	-	-	-	2 35	2 64	2 47	1 70	-	1 22	-	2 65	
RF340R	2/107	5 100	5 60	5 110	5 80	2 100	-	-	_	-	_	2 40	2 60	2 55	2 55	-	2 18	_	2 85	
RF350R with ANT 1	2/109	5 100	5 80	5 110	5 95	2 110	-	-	-	-	-	2 50	2 65	2 70	2 60	-	2 23	-	2 90	
RF350R with ANT 3	2/109	-	-	-	-	-	-	-	1 12	-	-	0 25	0 35	2 32	0 42	-	0 16	-	-	
RF350R with ANT 3S	2/109	-	-	-	-	-	04	-	-	-	-	-	-	-	-	-	-	-	-	
RF350R with ANT 12	2/109	-	-	-	-	-	0 3	-	-	-	-	-	-	-	-	-	-	-	-	
RF350R with ANT 18	2/109	-	-	-	-	-	0 6	-	1 10	-	-	-	2 24	1 22	1 27	-	1 9	-	-	
RF350R with ANT 30	2/109	1 45	1 40	1 50	1 45	-	-	-	0 15	-	-	2 30	1 35	1 35	0 45	-	1 14	-	0 47	
RF380R	2/112	5 170	5 120	5 170	5 150	2 200	-	-	-	-	-	5 75	1 120	2 96	2 120	-	2 32	-	2 145	
RF382R	2/115	-	-	-	-	-	-	-	-	-	-	-	40 65	40 65	40 65	-	-	-	-	
MOBY D reader	2/122																			
SLG D11 / SLG D11S with ANT D2	2/123	-	-	-	-	-	-	-	-	-	-	-	45 70	35 60	45 70	-	-	-	-	
SLG D11 / SLG D11S with ANT D5	2/123	0 220	0 200	0 300	0 220	0 240	-	-	-	-	-	-	0 150	0 120	0 150	-	-	-	0 200	
SLG D12 / SLG D12S	2/126	0 120	0 100	0 160	0 120	0 100	-	-	-	-	-	-	0 70	0 60	0 70	-	-	-	0 100	

- Reader-transponder combination not released.

																		Overview
MDS D426 6GT2600–	MDS D526 6GT2600-	MDS D117 6GT2600-	MDS D127 6GT2600-	MDS D428 6GT2600-	MDS D528 6GT2600–	MDS D139 6GT2600–	MDS D339 6GT2600-	MDS D160 6GT2600-	MDS D460 6GT2600–	RF320T 6GT2800–	RF330T 6GT2800–	RF340T 6GT2800–	RF350T 6GT2800–	RF360T 6GT2800–	RF370T 6GT2800–	RF380T 6GT2800–	Transponder <i>O</i> Article No. (<i>n</i>	perating distance nm) between trans-
4AH00	5AH00	0AG00	0AF00	4AK00-0AX0	5AK00	0AA10	3AA10	0AB10	4AB00	1CA00	5BA00	4BB00	5BD00	4AC00	5BE00 (32Kb) 6BE00 (64Kb)	5DA00	po	onder and reader
SIEMENS GTI2000 ALAGO MOS D126 MOS D126 MOS YD ALA	SIEMENS 6GT2000-SAH00 MOS D526 AS: A	•				•		SUEM ENS SETTICO-GARDO ADS DIDO ACRY D	SIEMENS 6672600-4A800 WDS D460 WOBY D		$\overline{\mathbf{\cdot}}$	s presta Britant Britant	STEROIERS SIMATIC SSOT strate-mass **	SIEMENS SIMATIC RF380T www.macace				
2 Kbyte	8 kbyte	112 byte	112 byte	2 kbyte	8 kbyte	112 byte	992 byte	112 byte	2 kbyte	20 byte	32 kbyte	8 kbyte	32 kbyte	8 kbyte	32 / 64 kbyte	32 kbyte	User memory	
-40 °C	-40 °C	-40 °C	-40 °C	-40 °C	-40 °C	-40 °C 220 °C	-40 °C 220 °C	-40 °C 175 °C	-40 °C	-40 °C 140 °C	-40 °C	-40 °C 85 °C	-40 °C	-40 °C	-40 °C 85 °C	-40 °C 220 °C	Temperature rar	nge
Ø 50 x 3.6	Ø 50 x 3.6	Ø 4 x 5	Ø 6 x 5	Ø 18 x 20	Ø 24 x 20	Ø 85 x 15	Ø 85 x 15	Ø 16 x 3	Ø 16 x 3	Ø 27 x 4	Ø 30 x 8	48 x 25 x 15	50 x 50 x 20	85.8 x 54.1 x	75 x 75 x 41	Ø 114 x 83	L x W x H or Ø x	(H (mm)
2/40	2/42	2/44	2/46	2/48	2/50	2/52	2/54	2/56	2/58	2/61	2/63	2/65	2/67	2.5	2/71	2/73	Page	
2/40	2/42	2/44	2/40	2/40	2/30	2/32	2/34	2/30	2/30	2/01	2/05	2/03	2/01	2/05	2// 1	2115	2/78 RF200 re	ader
_	_	_	0 2	1 10	1 10	_	_	1 10	1 8	_	_	_	_	_	_	_	2/79 BE210B	auer
2 25	2 25	_	-	1 18	1 15	5 35	2 15	1 20	1 18	_	_	_	_	_	_	_	2/83 BE220B	
2 45	2 45	_	_	1 30	1 30	5 77	0 35	1 33	1 30	_	_	_	_	_	_	_	2/86 BE240B	
_	2 35	_	_	0 25	1 20	_	-	1 16	0 18	_	_	_	_	_	_	_	2/90 BE250B	with ANT 3
-	_	0 2	0 2	_	_	_	_	_	_	_	_	_	_	_	_	_	2/90 RF250R	with ANT 3S
_	_	0 2	0 3	_	_	-	_	_	_	-	_	_	_	-	-	_	2/90 RF250R	with ANT 8
_	_	03	0 4	1 8	1 8	-	_	0 12	1 10	-	_	_	_	_	-	-	2/90 RF250R	with ANT 12
_	-	_	-	1 18	1 15	_	-	1 18	1 17	_	-	_	-	_	-	_	2/90 RF250R	with ANT 18
0 44	2 35	-	-	1 20	1 20	1 42	1 42	1 23	1 21	-	-	-	-	-	-	_	2/90 RF250R	with ANT 30
2 70	2 70	-	-	2 40	2 35	2 80	5 65	2 40	2 40	-	-	-	_	-	-	-	2/95 RF260R	
5 100	5 100	-	-	0 55	0 55	5 160	5 130	0 65	0 60	-	-	-	-	-	-	-	2/99 RF290R	with ANT D1
0 300	0 300	-	-	-	-	0 400	0 300	0 130	0 120	-	-	-	-	-	-	-	2/99 RF290R	with ANT D5
0 350	0 350	-	-	-	-	0 500	0 400	0 130	-	-	-	-	_	-	-	-	2/99 RF290R	with ANT D6
0 350	0 350	-	-	-	-	0 450	0 300	0 130	-	-	-	-	_	-	-	-	2/99 RF290R	with ANT D10
																	2/104 RF300 re	ader
5 100	-	-	-	1 43	-	5 96	5 74	1 39	1 37	1 23	0 5	2 36	2 47	2 60	-	-	2/105 RF310R	
0 80	-	-	-	2 35	-	5 80	5 75	2 35	2 25	1 20	-	2 50	2 60	2 65	5 60	5 80	2/107 RF340R	
0 85	-	-	-	2 35	-	5 85	5 90	2 35	2 35	1 30	-	2 55	2 65	2 75	5 65	5 90	2/109 RF350R	with ANT 1
-	-	-	-	0 25	-	5 85	-	1 16	0 18	1 16	1 12	2 32	2 35	2 40	-	-	2/109 RF350R v	with ANT 3
-	-	0 2	0 2	-	-	-	-	-	-	-	-	-	-	-	-	-	2/109 RF350R v	with ANT 3S
-	-	0 3	0 3	1 10	-	-	-	0 8	1 10	-	0 4	-	-	1 5	-	-	2/109 RF350R v	with ANT 12
-	-	1 3	0 4	1 12	-	-	-	118	1 12	0 10	0 10	0 20	-	2 15	-	-	2/109 RF350R v	with ANT 18
0 45	-	-	-	1 25	-	-	-	1 25	1 18	0 15	2 13	0 30	0 35	2 25	-	-	2/109 RF350R v	with ANT 30
0 155	-	-	-	2 70	-	5 160	5 160	2 64	2 65	2 45	-	2 80	2 100	2 120	5 100	5 125	2/112 RF380R	
-	-	-	-	-	-	-	-	35 50	30 50	-	-	-	-	-	-	-	2/115 RF382R	
																	2/122 MOBY D	reader
-	-	-	-	-	-	-	-	35 55	35 50	-	-	-	-	-	-	-	2/123 SLG D11 with ANT	/ SLG D11S D2
-	-	-	-	0 70	-	0 280	-	0 75	0 70	-	-	-	-	-	-	-	2/123 SLG D11 with ANT	/ SLG D11S D5
-	-	-	-	0 40	-	0 120	-	0 45	0 40	-	-	-	-	-	-	-	2/126 SLG D12	/ SLG D12S

SIMATIC Ident RFID systems field data table

SIMATIC Ident RFID systems field data table

UHF range (RF600)

Overview

Maximum read distance (m)	Transponder Article No.	RF622L 6GT2810– 4AC80	RF630L 6GT2810– 2AB00	RF630L 6GT2810- 2AB01	RF630L 6GT2810- 2AE81-0AX1	RF630L 6GT2810– 2AB02–0AX0	RF630L 6GT2810- 2AB03	RF640L 6GT2810- 2AC00 6GT2810- 2AC10	RF680L 6GT2810– 2AG80	RF690L 6GT2810– 2AG00 6GT2810– 2AG10	RF610T 6GT2810- 2BB80 6GT2810- 2BB80-0AX1	RF620T 6GT2810– 2HC81	RF6 6GT281/	522T 0–4HC80
			e3							<u> </u>		•		¢
EPC ID memory		62 byte	12 byte	12 byte	16 byte	16 byte	30 byte	12/60 byte	30 byte	12/60 byte	30 byte	16 byte	62	byte
User memory		3 424 byte	12 byte	12 byte	16 byte	64 byte	64 byte	64/16 byte	64 byte	64/16 byte	64 byte	64 byte	3 424	4 byte
L x W x H or Ø x H (mm)		90 x 18 x 0.5	101 x 152 x 0.3	101 x 50 x 0.3	90 x 30 x 0.3	27 x 97 x 0.3	34 x 54 x 0.3	50 x 22 x 1.6	54 x 86 x 0.4	88 x 25 x 1.6	54 x 86 x 0.4	127 x 38 x 6	120 x 3	30 x 6.5
Frequency range MHz		860 - 960	860 - 960	860 – 960	860 - 960	860 – 960	860 – 960	860 – 868 902 – 928	860 - 960	860 – 868 902 – 928	860 – 960	860 – 960	860 – 960	
	Page	3/5	3/6	3/6	3/6	3/6	3/6	3/9	3/11	3/12	3/14	3/16	3/18	3/18
													Metal-free surface	With spacer on metal
RF650R reader														
RF650R with RF620A	3/30	0.4	0.95	0.95	0.6	0.95	0.6	0.35	0.6	0.6	0.6	0.6	0.4	0.2
RF650R with RF640A	3/30	2.5	4.6	4.6	2.3	4.6	3.0	2.0	2.3	2.3	3.0	4.6	2.5	0.7
RF650R with RF642A	3/30	3.0	8.0	8.0	4.0	8.0	5.0	2.5	4.0	4.0	5.0	8.0	3.0	1.0
RF650R with RF660A	3/30	3.0	8.0	8.0	4.0	8.0	5.0	3.5	4.0	4.0	5.0	8.0	3.0	0.9
RF680R reader														
RF680R with RF620A	3/33	0.4	1.35	1.35	0.85	1.35	0.85	0.35	0.85	0.7	0.85	0.85	0.4	0.2
RF680R with RF640A	3/33	2.5	6.0	6.0	3.0	6.0	4.0	2.0	3.0	3.0	4.0	6.0	2.5	0.7
RF680R with RF642A	3/33	3.0	8.0	8.0	4.0	8.0	5.0	2.5	4.0	4.5	5.0	8.0	3.0	1.0
RF680R with RF660A	3/33	3.0	8.0	8.0	4.0	8.0	5.0	3.5	4.0	5.0	5.0	8.0	3.0	0.9
RF685R reader														
RF685R with internal anternal	enna 3/37	3.0	7.0	7.0	3.5	7.0	4.0	3.0	3.5	4.0	4.5	7.0	3.0	0.9
RF685R with RF620A	3/37	0.4	1.35	1.35	0.85	1.35	0.85	0.35	0.85	0.7	0.85	0.85	0.4	0.2
RF685R with RF640A	3/37	2.5	6.0	6.0	3.0	6.0	4.0	2.0	3.0	3.0	4.0	64.0	2.5	0.7
RF685R with RF642A	3/37	3.0	8.0	8.0	4.0	8.0	5.0	2.5	4.0	4.5	5.0	58.0	3.0	1.0
RF685R with RF660A	3/37	3.0	8.0	8.0	4.0	8.0	5.0	3.5	4.0	5.0	5.0	8.0	3.0	0.9

RF625T	RF630T	RF640T	RF680T		
6GT2810- 2EE00	6GT2810- 2EC00	6GT2810- 2DC00	6GT2810– 2HG80		
6GT2810– 2EE01	6GT2810- 2EC10	6GT2810- 2DC10			
•	ð		•		
16 byte	30 byte	30 byte	30 byte		
64 byte	64 byte	64 byte	64 byte		
Ø 30 x 8	Ø 30 x 8	Ø 50 x 8	32 x 130 x 15		
860 - 868 902 - 928	860 – 868 902 – 928	860 – 868 902 – 928	860 - 960		
3/20	3/22	3/24	3/26		

0.6	0.3	0.6	0.6
4.6	1.5	3.0	3.0
8.0	2.0	4.0	4.0
8.0	2.0	4.0	4.0
0.5	0.4	0.9	0.9
1.2	2.0	4.0	4.0
1.5	2.0	4.0	4.0
1.5	2.0	4.0	4.0
1.5	2.0	4.0	4.0
0.5	0.4	0.9	0.9
1.2	2.0	4.0	4.0
1.5	2.0	4.0	4.0
1.5	2.0	4.0	4.0





2/2	Introduction	2/102	RF300
2//	Transponders (ISO mode)	2/104	RF300 readers
2/4	Introduction	2/105	RF310R
2/3	MDS D165	2/107	RF340R
2/8	MDS D261	2/109	RF350R
2/10	MDS D100	2/112	RF380R
2/12	MDS D200	2/115	RF382R
2/14	MDS D400	2/117	RF350M mobile handheld terminal
2/16	MDS D421	2/120	MOBY D
2/18	MDS D521	2/122	MOBY D readers
2/20	MDS D422	2/123	SLG D11 / SLG D11S basic units
2/22	MDS D522	2/126	SLG D12 / SLG D12S
2/24	MDS D423	2/129	MOBY D Configuring instructions
2/26	MDS D124	2, 120	
2/28	MDS D324	2/130	HF antennas
2/30	MDS D424	2/130	Introduction
2/32	MDS D524	2/131	ANT 1 for RF350R
2/34	MDS D425	2/132	ANT 3 for RF250R, RF350R and RF350M
2/36	MDS D525	2/133	ANT 3S for RF250R, RF350R and
2/38	MDS D126	0/10/	RF350M
2/40	MDS D426	2/134	ANT 8 for RF250R and RF350M
2/42	MDS D526	2/136	ANT 12 for RF250R, RF350R and RF350M
2/44	MDS D117	2/137	ANT 18 for RF250R, RF350R and RF350M
2/46	MDS D127	2/138	ANT 30 for RF250R, RF350R and RF350M
2/48	MDS D428	2/139	ANT DI TOT RE290R
2/50	MDS D528	2/140	ANT D2 for SLG D11/SLG D115
2/52	MDS D139	2/141	ANT D5 for RF290R and SLG DTT/DTTS
2/54	MDS D339	2/143	
2/56	MDS D160	2/145	ANT DTU for RF290R
2/58	MDS D460		
2/60	Transponders (BE300 mode)		
2/60	Introduction		
2/61	BE320T		
2/63	BE330T		
2/65	BE340T		
2/67	BE350T		
2/69	BE360T		
2/71	BE370T		
2/73	RF380T		
2/76	PE200		
2/70	RE200 readers		
2/78	<u>PE210P</u>		
2/19	RE210M mobile handhold terminal		
2/02			
2/03			
2/00	RE250R		
2/90	RE260R		
2/90	RE200R		
2/99	RE350M mobile handhold terminal		
2/11/			

Introduction

Overview



As the world's leading supplier of identification systems, with SIMATIC Ident Siemens offers a unique integrated and scalable rance of RFID and optical identification systems for flexible and cost-effective identification solutions.

RFID systems are offered for the most diverse requirements on performance, range, frequency range as well as HF and UHF. This section provides you an overview of our RFID systems in the HF range.

Easy integration of the RFID systems via communication modules and pre-configured software blocks in the world of Totally Integrated Automation (TIA) significantly reduces the work and costs necessary for commissioning, diagnostics and maintenance. Thanks to many years of experience in the area of RFID. Siemens is a competent partner for implementation of the most diverse solutions in all sectors, but especially in the areas of production and logistics.

RFID systems for the HF frequency range

Siemens offers the following two RFID systems for the HF range:

- SIMATIC RF200: The compact and economical RFID system according to ISO 15693. Readers with an IO-Link interface are provided for particularly simple and open identification solutions.
- SIMATIC RE300:
- For the most demanding requirements in terms of speed, data volume and diagnostics functionality, the RF300 mode with separate transponders is available. The high-performance RFID system can be operated with ISO 15693 transponders to meet average performance requirements.

Meaningful data from the outset

The RFID systems ensure that meaningful data accompanies a product or object from the very beginning. The transponders are attached to the product, product carrier, object or its transport or packing unit and are recorded, read and written by non-contact methods. This means that all the application-specific data is located on the transponder. This is true whether you are dealing with vehicle body parts in the automotive industry or order picking boxes. Up to 64 KB of data can be stored and individually read and supplemented when required at the various workstations or manufacturing stations. This all means that the flow of material and data is synchronized optimally.

Contactless data transfer and a high degree of industrial compatibility

Powerful readers (write/read devices) in various rugged designs ensure fast and reliable data transfer between the transponders and the higher-level systems (e.g. PLC, PC).

The data and power are transmitted inductively by an electromagnetic alternating field. This principle of contactless data transfer also works in the presence of contamination or through numerous non-metallic materials.

Perfectly matched components

The RFID systems consist of perfectly matched individual components:

- Transponder
- Readers
- Antennas
- Communication modules for connection to the automation system (e.g. PROFIBUS, PROFINET)
- Software for system integration

For a wide range of applications in all sectors

- Production control
- Asset management
- Tracking & tracing

Wide range of transponders

A wide range of different transponders is available using a variety of storage technologies and geometric designs. Their strength is not only their high level of data security but also the excellent high degree of protection against ambient conditions such as contamination, temperature fluctuations, washing water or shock load.

Benefits



- Flexible and economic solutions thanks to the complete and scalable portfolio for the field of industrial identification.
- Simplified engineering, commissioning, diagnostics and maintenance through seamless integration into Totally Integrated Automation:
- Integrated bus connection to an automation system, such as SIMATIC, SIMOTION or SINUMERIK via communication modules with PROFIBUS and PROFINET.
- Simple S7 software integration via ready-to-use function blocks.
- Extensive status and diagnostic functions.
- High degree of investment protection thanks to:
 - Open standards (e.g. ISO 15693). Software compatibility between the RFID and optical reading
 - systems of Siemens. Standardized communication interfaces.
- Openness through connection possibilities to different bus systems from different manufacturers and PC environments via communication modules.
- Worldwide Service and Support.

Integration

A wide range of communication modules, function blocks, as well as high-performance drivers and function libraries permits easy and quick integration into the application. And best of all: SIMATIC RF is part of Totally Integrated Automation (TIA) and can be integrated easily and cost-effectively into the SIMATIC world. For more details on the connection possibilities, see the section "Communication Modules".

SIMATIC Ident Configuration Guide

Here is a compact configuration tool for setting up RFID systems:

http://support.automation.siemens.com/WW/view/en/67384964

Transponders (ISO mode)

Introduction

Overview

The following transponders can be used with the SIMATIC RF200, RF300 or MOBY D RFID systems:

Transponder	Features	Page	Transponder	Features	Page
MDS D165	SmartLabel, (PET) similar to credit card format. Applications range from simple identifica- tion such as electronic barcode substitu- tion or supplementation, to storage and distribution logistics, right up to product identification Usable for RFID systems: • RF200 • RF300 • MOBY D	2/8	MDS D421	Transponder for the tool coding according to DIN 69873. It can be used wherever very small data media and exact positioning are required (e.g. for tool identification). Usable for RFID systems: • RF200 • RF300 • MOBY D	2/16
MDS D261	SmartLabel, (PET) in compact design. Applications range from simple identifica- tion such as electronic barcode substitu- tion or supplementation, to storage and distribution logistics, right up to product identification. Usable for RFID systems: • RF200 • RF300 • MOBY D	2/8	MDS D521	The MDS D521 is designed for tool coding according to DIN 69873. Usable for RFID systems: • RF200	2/18
MDS D100	Universal transponder in credit card format with 112 bytes EEPROM, suitable for the identification of transport units in production-related logistics. Usable for RFID systems: • RF200 • RF300 • MOBY D	2/10	MDS D422	Transponder for the identification of metallic workpiece holders, workpieces or containers. Usable for RFID systems: • RF200 • RF300	2/20
MDS D200	Universal transponder in credit card format with 256 bytes EEPROM, suitable for the identification of transport units in production-related logistics. Usable for RFID systems: • RF200 • RF300 • MOBY D	2/12	MDS D522	Transponder for the identification of metallic workpiece holders, workpieces or containers. Usable for RFID systems: • RF200	2/22
MDS D400	Universal transponder in credit card format with 2 000 bytes FRAM, suitable for the identification of transport units in production-related logistics. Usable for RFID systems:	2/14	6612600 5AF00 0AX0 MDS D522 A5 A		
	• RF200 • RF300 • MOBY D		MDS D423	Rugged transponder for use in production and distribution logistics as well as in assembly and production lines. Usable for RFID systems: • RF200 • RF300	2/24

RFID systems for the HF range Transponders (ISO mode)

Transmander	Fachures	Deme	Transmonder	Freedomen	Derre
Iransponder MDS D124	Heat-resistant transponder for use in	2/26	Iransponder MDS D525	It is designed for use in assembly and	2/36
MOS DI24	applications with high thermal stress. Usable for RFID systems: • RF200 • RF300 • MOBY D		SIEMENS GT2800-5AG00 MDS D525 AS A	production lines as well as in the powertrain sector. Usable for RFID systems: • RF200	
MDS D324	Rugged transponder for use in harsh industrial environments and under extreme environmental conditions. Usable for RFID systems: • RF200 • RF300 • MOBY D	2/28	MDS D126 SIEMENS 6GT2600-0AE00 MDS D126 MOBY D A3: A	Compact and rugged transponder for identification of transport units in production-related logistics. The transponder can also be used in harsh environments. Usable for RFID systems: • RF200 • RF300 • MOBY D	2/38
MDS D424	Rugged transponder for use in production and distribution logistics as well as in assembly and production lines. Usable for RFID systems: • RF200 • RF300 • MOBY D	2/30	MDS D426 SIEMENS 6GT2600-4AH00 MDS D426 MOS D426 MOS V A8: A	Compact and rugged transponder for identification of transport units in production-related logistics. The transponder can also be used in harsh environments. Usable for RFID systems: • RF200 • RF300 • MOBY D	2/40
MDS D524	The transponder is designed for use in production and distribution logistics as well as in assembly and production lines. Usable for RFID systems: • RF200	2/32	MDS D526 SIEMENS 6GT2600-SAH00 MDS D526 AS: A	It is designed for the identification of transport units in production-related logistics. Usable for RFID systems: • RF200	2/42
MDS D425	Compact and rugged transponder suitable for screw mounting. For use in assembly and production lines in the powertrain sector. Usable for RFID systems: • RF200 • RF300	2/34	MDS D117	Extremely small, ISO-15693-compatible transponder that can be flush-mounted on metal with adhesive. Transponder for direct identification of metallic workpiece holders, small workpieces, or containers. Usable for RFID systems: • RF200 • RF300	2/44

RFID systems for the HF range Transponders (ISO mode)

Introduction

2

Transponder	Features	Page	Transponder	Features	Page
MDS D127	Extremely small, ISO 15693-compatible transponder that can be screwed flush into metal. Transponder for direct identification of metallic workpiece holders, small workpieces, or containers Usable for RFID systems: • RF200 • RF300	2/46	MDS D160 SLELALENS GGT2600-0AB00 MOS D180 MOSY D	Special transponder for harsh environ- ments in the laundry and cleaning industry. Usable for RFID systems: • RF200 • RF300 • MOBY D	2/56
MDS D428	Compact and rugged transponder for screw mounting; for use in assembly and production lines in the powertrain area. Usable for RFID systems: • RF200 • RF300 • MOBY D	2/48	MDS D460 SIEMENS 6GT2600-4AB00 WDS D460 WOBY D	Rugged transponder for use in assembly lines. Usable for RFID systems: • RF200 • RF300 • MOBY D	2/58
MDS D528	It is designed for use in assembly and production lines as well as in the powertrain sector. Usable for RFID systems: • RF200	2/50	<i>Customer-specific</i> Customer-specific t range, geometry, et	e transponders ransponders (packaging, temperatu c.) on request.	re
MDS D139	Heat-resistant transponder for use in paint shops or applications with high thermal stress. Usable for RFID systems: • RF200 • RF300 • MOBY D	2/52			
MDS D339	Heat-resistant transponder for use in paint shops or applications with high thermal stress Usable for RFID systems: • RF200 • RF300 • MOBY D	2/54			

Introduction

Benefits



The comprehensive portfolio of ISO 15693 transponders offers the right solution for every requirement in production and production logistics:

- Large memory of up to 8 192 bytes (FRAM)
- Low-cost transponders can, if necessary, be mounted on metal with a spacer.
- Extremely rugged transponder for high temperature ranges up to 220 °C with ATEX approval for use in paint shops.
- Extremely small transponder for exact positioning, e.g. for tool identification.
- Screw-fit transponders for automatic attachment by means of robots.
- Screw-fit transponders for flush-mounting in metal for identifying workpieces or workpiece holders.
- Customized solutions for SmartLabels and transponders on request.

Technical specifications

Field data (operating/limit distance) of transponders and readers (all specifications in mm)

The the field data (unaffected by metal) for all ISO transponders (MDS Dxxx) in connection with RF200 readers is listed in the technical specifications of the RFID overview. The listed technical data are typical values and are valid for a room temperature of +25 °C.

Transponder (ISO mode)

Overview



The SmartLabels MDS D165 and MDS D261 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

SmartLabels permit numerous flexible constructions to ensure optimum dimensioning for many different applications.

Thanks to their very reasonable price, the SmartLabels can be used universally as "electronic barcode substitutes or supplements" or "delivery notes".



Technical specifications

Article number	6GT2600-1AB00-0AX0	6GT2600-1AA01-0AX0
Product type designation	MDS D165 SmartLabel	MDS D261 SmartLabel
Suitability for operation	RF200, RF300, MOBY D	RF200, RF300, MOBY D
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	500 mm	450 mm
	range is reader dependent: observe http://support.automat	ion.siemens.com/WW/view/en/67384964
Protocol with radio transmission	ISO 15693	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	Yes	Yes
Product component Backup battery	No	No
Memory		
Type of memory	EEPROM	EEPROM
Storage capacity of the user memory	112 byte	256 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 112 bytes, configuration memory 8 bytes	UID (fixed code) 8 bytes, user memory 256 bytes, configuration memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 у	10 y
Property of memory	Block-by-block write protection of the user memory	Block-by-block write protection of the user memory
Type of transponder chip used	NXP I-Code SLI	STM LRI2K
Mechanical data		
Material	Top side + inlay: PET, antenna aluminum	Top side + inlay: PET, antenna aluminum
Color	white	white
Mounting distance relating to metal surfaces recommended minimum	25 mm	25 mm

RFID systems for the HF range Transponder (ISO mode)

MDS D165/D261

Article number	6GT2600-1AB00-0AX0	6GT2600-1AA01-0AX0
Product type designation	MDS D165 SmartLabel	MDS D261 SmartLabel
Suitability for operation	RF200, RF300, MOBY D	RF200, RF300, MOBY D
Permitted ambient conditions		
Ambient temperature		
 during read/write access 	-25 +85 °C	-25 +85 °C
 outside the read/write area 	-25 +85 °C	-25 +85 °C
 during storage 	20 30 °C	20 30 °C
Protection class IP	IP65	IP65
Resistance to mechanical stress	Maximum storage period: 2 years (determined by durability of the adhesive)	Maximum storage period: 2 years (determined by durability of the adhesive)
Design, dimensions and weight		
Width	54 mm	55 mm
Height	0.3 mm	0.3 mm
Depth	86 mm	55 mm
Net weight	1 g	1 g
Mounting type	one-side adhesible	one-side adhesible
Product properties, functions, components general		
Product feature		
 printable 	Yes	Yes
Printing process	Thermal transfer process	Thermal transfer process

Selection and ordering data

	Article No.
MDS D165 SmartLabel	6GT2600-1AB00-0AX0
112 bytes EEPROM	
Ordering quantity 1 000 units or a multiple thereof.	
MDS D261 SmartLabel	6GT2600-1AA01-0AX0
256 bytes EEPROM	
Ordering quantity 1 000 units or a multiple thereof.	

Transponder (ISO mode)

Overview



The transponder in credit card format can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

Applications range from simple identification such as electronic bar code substitution or supplementation, to storage and distribution logistics, up to product identification.

This transponder can even be used problem-free under extreme environmental conditions (e.g. when subjected to temperatures up to +80 $^\circ$ C).

Technical specifications

Article number	6GT2600-0AD10
Product type designation	MDS D100 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	650 mm; range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	112 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 112 bytes, configuration memory 8 bytes
Number of read cycles	100 000 000 000 000
at ambient temperature < 40 °C maximum	
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time	10 y
at ambient temperature < 40 °C not less than	,
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	NXP I-Code SLI
Mechanical data	
Material	PC laminated plastic
Color	white / petrol
Mounting distance relating to metal surfaces recommended minimum	20 mm
Permitted ambient conditions	
Ambient temperature	25 00.00
during read/write access	-25 +80 °C
outside the read/write area	-25 +80 °C
during storage	-25 +80 °C
Protection class IP	
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Resistance to mechanical stress	Shock and vibration according to ISO 10373 / ISO 7810, torsion and twisting according to ISO 10373 / ISO 7816-3
Design, dimensions and weight	
Width	54 mm
Height	0.9 mm
Depth	85.6 mm
Net weight	5 g
Mounting type	Gluing, mounting bag (see accessories)
Product properties, functions, components general	
Product feature	
printable	Yes
Printing process	Printable on both sides
Standards, specifications,	
MTRF	228 v
Accessories	
Accessories	Fixing strap, holder, spacer
	.g

Transponder (ISO mode)



Transponder (ISO mode)

Overview





The MDS D200 is a mobile, passive, maintenance-free transponder based on ISO 15693.

The MDS D200 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

From simple identification, e.g. as electronic barcode replacement or supplementation, through warehouse and distribution logistics, up to product identification.

Technical specifications

0
er
D
ident: observe
4

Article number	6GT2600-1AD00-0AX0
Product type designation	MDS D200 transponder
Suitability for operation	
Memory	11 200, 11 300, 110 11 0
Type of memory	FEPROM
Storage capacity of the user memory	256 byte
Type of memory organization	LIID (fixed code) 8 bytes u
type of memory organization	ser memory 256 bytes, configuration memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	TI Tag-it HFI
Mechanical data	
Material	PVC laminated plastic
Color	white
surfaces recommended minimum	25 mm
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-20 +60 °C
 outside the read/write area 	-20 +60 °C
during storage	-20 +60 °C
Protection class IP	IP67
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Resistance to mechanical stress	Shock and vibration according to ISO 10373 / ISO 7810, torsion and twisting according to ISO 10373 / ISO 7816-3
Design, dimensions and weight	
Width	54 mm
Height	0.8 mm
Depth	85 mm
Net weight	5 g
Mounting type	Gluing, mounting bag (see accessories)
Product properties, functions, components general	
Product feature	
printable	Yes
Printing process	Printable on both sides
Standards, specifications,	
approvals	
MIBF	228 у
Accessories	Division strain, la dala
Accessories	Fixing strap, holder, spacer

RFID systems for the HF range Transponder (ISO mode)

		MDS D200
Selection and ordering data		Dimensional drawings
	Article No.	-
MDS D200 transponder 256 bytes EEPROM Ordering quantity 250 units or a multiple thereof.	6GT2600-1AD00-0AX0	85.6 ± 0.2
Accessories		
Fixing pocket	6GT2190-0AB00	
For MDS D200, usable together with spacer 6GT2190-0AA00.		++++0.2
Ordering quantity 50 units or a multiple thereof.		
Spacer	6GT2190-0AA00	
For fixing pocket (6GT2190-0AB00), thickness 20 mm		MDS D200 transponder
The purpose of the spacer is to maintain the recommended dis- tance to the metal when installing the transponder.		
Ordering quantity 50 units or a multiple thereof.		
Holder	6GT2390-0AA00	
For MDS D200. Ordering quantity 50 units or a multiple thereof.		

Transponder (ISO mode)

Overview

MDS D400



The MDS D400 is a passive, maintenance-free transponder based on the ISO standard 15693 with FRAM technology.

650 mm

The MDS D400 transponder can be used for the RFID system MOBY D as well as for SIMATIC RF300 (ISO mode) and SIMATIC RF200.

Application

ISO transponder, suitable for the identification of transport units in production-related logistics.

Technical specifications Article number 6GT2600-4AD00 MDS D400 transponder Product type designation Suitability for operation RF200, RF300, MOBY D Wireless frequencies Operating frequency Rated value 13.56 MHz **Electrical data** Range maximum 650 mm; range is reader dependent: observe http://support.automation.siemens.com/WW/view/en/67384964 Protocol with radio transmission ISO 15693 Transfer rate with radio transmission 26.5 kbit/s maximum Product feature multitag-capable Yes Product component Backup battery No Memory Type of memory FRAM Storage capacity of the user memory 2 000 byte Type of memory organization UID (fixed code) 8 bytes, user memory 2 000 bytes configuration memory 40 bytes Number of read cycles 1 000 000 000 000 at ambient temperature < 40 °C maximum 1 000 000 000 000 Number of write cycles at ambient temperature < 40 °C maximum Data retention time 10 y at ambient temperature < 40 °C not less than Block-by-block write protection of Property of memory the user memory Fujitsu MB89R118 Type of transponder chip used Mechanical data Material PVC laminated plastic white Color Mounting distance relating to metal surfaces recommended minimum 20 mm Permitted ambient conditions Ambient temperature • during read/write access -20 ... +60 °C -20 ... +60 °C · outside the read/write area -20 ... +60 °C during storage IP67 Protection class IP According to DIN EN 60721-3-7 Class 7 M3 Shock resistance Resistance to mechanical stress acc. to ISO 10373/ ISO 7816-1 Design, dimensions and weight Width 54 mm Height 0.8 mm 85.6 mm Depth 5 g Net weight gluing, mounting bag (see accessories) Mounting type Product properties, functions, components general Product feature printable Yes Printable on both sides Printing process Standards, specifications, approvals MTBF 228 y Accessories Accessories Fixing strap, holder, spacer

Transponder (ISO mode)

MDS D400



Siemens ID 10 · 2016 2/15

Transponder (ISO mode)

MDS D421

Overview





The MDS D421 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

Note

This transponder is used exclusively with the following readers/antennas:

- RF210R
- RF250R with ANT 8, ANT 12 or ANT 18
- RF350R with ANT 12 or ANT 18
- RF350M with external antenna

Application

The MDS D421 is designed for tool coding according to DIN 69873.

It can be used wherever small transponders and exact positioning are required, for example, for tool identification or on workpiece holders.

Technical specifications

Article number	6CT2600 44E00			
Product type designation	MDS D421 transponder			
	RF200, RF300			
wireless frequencies	10 50 141			
Operating frequency Rated value	13.56 MHZ			
Electrical data				
Range maximum	8 mm; range is reader dependent: observe			
http://support.automation.siemens.com	n/WW/view/en/67384964			
Protocol with radio transmission	ISO 15693			
Transfer rate with radio transmission maximum	26.5 kbit/s			
Product feature multitag-capable	Yes			
Product component Backup battery	No			
Memory				
Type of memory	FRAM			
Storage capacity of the user memory	2 000 byte			
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes			
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000			
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000			
Data retention time at ambient temperature < 40 °C not less than	10 у			
Property of memory	Block-by-block write protection of the user memory			
Type of transponder chip used	Fujitsu MB89R118			
Mechanical data				
Material	Epoxy resin			
Color	black			
Mounting distance relating to metal surfaces recommended minimum	0 mm			
Permitted ambient conditions				
Ambient temperature				
 during read/write access 	-25 +85 °C			
 outside the read/write area 	-40 +100 °C			
 during storage 	-40 +100 °C			
Protection class IP	IP67 / IPx9K			
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3			
Shock acceleration	1 000 m/s ²			
Vibrational acceleration	200 m/s ²			
Design, dimensions and weight				
Height	4.5 mm			
Diameter	10 mm			
Net weight	1 g			
Mounting type	gluing			
Product properties, functions, components general				
Product feature				
• silicon-free	Yes			
• printable	No			
Selection and ordering dat	ta	Dimensional drawings		
---	---------------	----------------------	-----	--
	Article No.			
MDS D421 transponder	6GT2600-4AE00			
2 000 bytes FRAM			4.5	
Ordering quantity 10 units or a nultiple thereof.				

Transponder (ISO mode)

MDS D521

Overview





The MDS D521 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can only be operated with the SIMATIC RF200 RFID system.

Application

The MDS D521 is designed for tool coding according to DIN 69873.

It can be used wherever small transponders and exact positioning are required, for example, for tool identification or on workpiece holders.

Article number	6GT2600-5AF00
Product type designation	MDS D521 transponder
Suitability for operation	RE200
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	5 mm; range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	8 192 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 8 192 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 у
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R112
Mechanical data	
Material	Epoxy resin
Color	black
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
during read/write access	-25 +85 °C
outside the read/write area	-40 +100 °C
during storage	-40 +100 °C
Protection class IP Shock resistance	IP67 / IPx9K According to DIN EN 60721-3-7
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	4.5 mm
Diameter	10 mm
Net weight	1 g
Mounting type	gluing
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
 printable 	No

election and ordering dat	ta	Dimensional drawings		
	Article No.			
MDS D521 transponder	6GT2600-5AE00			
192 byte FRAM			4.5	
Ordering quantity 10 units or a nultiple thereof.				G FS10 XX 90462

Transponder (ISO mode)

MDS D422

Overview





The MDS D422 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can be operated with the SIMATIC RF200 and SIMATIC RF300 (ISO mode) RFID systems.

When operated with a mobile reader, the RF350M must be used with an external antenna.

Application

Identification of metallic workpiece holders, workpieces or containers.

Article pumper	
	6G12600-4AF00
Product type designation	MDS D422 transponder
Suitability for operation	RF200, RF300
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	19 mm; range is reader dependent: observe
http://support.automation.siemens.com	1/WW/VIew/en/67384964
Protocol with radio transmission	ISO 15693
Iransfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes
A ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature	1 000 000 000 000
Data retention time	10 v
at ambient temperature < 40 °C not less than	io y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Euliteu MB80B118
Type of transponder entp used	
Mechanical data	า มุแอน พบองสา 1 10
Mechanical data Material	PA6.6 GF / brass, nickel-plated
Mechanical data Material Color	PA6.6 GF / brass, nickel-plated black / silver
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum	PA6.6 GF / brass, nickel-plated black / silver 1 Nm
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C IP68
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C IP68 According to DIN EN 60721-3-7 Class 7 M3
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C IP68 According to DIN EN 60721-3-7 Class 7 M3 500 m/s ²
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C IP68 According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ²
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C IP68 According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ²
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C IP68 According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ²
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C IP68 According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 6 mm 20 mm
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C IP68 According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 6 mm 20 mm 13 g
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C IP68 According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 6 mm 20 mm 13 g gluing, screwing
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product properties, functions, components general	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C IP68 According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 6 mm 20 mm 13 g gluing, screwing
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product properties, functions, components general	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C IP68 According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 6 mm 20 mm 13 g gluing, screwing
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product properties, functions, components general Product feature • silicon-free	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C IP68 According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 6 mm 20 mm 13 g gluing, screwing
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product properties, functions, components general Product feature • silicon-free • printable	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C IP68 According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 6 mm 20 mm 13 g gluing, screwing Yes No
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product properties, functions, components general Product feature • silicon-free • printable Standards, specifications, approvals	PA6.6 GF / brass, nickel-plated black / silver 1 Nm 0 mm -25 +85 °C -40 +100 °C -40 +100 °C -40 +100 °C IP68 According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 6 mm 20 mm 13 g gluing, screwing Yes No

	Article No.	 		
DS D422 transponder	6GT2600-4AF00			
000 bytes FRAM				
ne installation tool is included in ach packing unit.		M20 × 1	6	
rdering quantity 5 units or a ultiple thereof.				a
				č

MDS D422 transponder

Transponder (ISO mode)

MDS D522

Overview





8 Kbyte	METAL	ISO

The MDS D522 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can only be operated with the RFID system SIMATIC RF200.

Operation with a mobile reader is currently only possible with RF210M.

Application

Identification of metallic workpiece holders, workpieces or containers.

Article number	6GT2600-5AF00	6GT2600-5AF00- 0AX0
Product type designation	MDS D522 transponder	MDS D522 transponder
	For gluing or screwing	For clipping
Suitability for operation	RF200	RF200
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	35 mm; range is reader dependent: observe	35 mm; range is reader dependent: observe
http://support.automation.siemens.	com/WW/view/en/673	384964
Protocol with radio transmission	ISO 15693	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	Yes	Yes
Product component Backup battery	No	No
Memory		
Type of memory	FRAM	FRAM
Storage capacity of the user memory	8 192 byte	8 192 byte
Type of memory organization	UID (fixed code) 8 bytes,	UID (fixed code) 8 bytes,
	user memory 8 192 bytes	user memory 8 192 bytes
	configuration	configuration
	memory 40 bytes	memory 48 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000	1 000 000 000 000
Data retention time	10 y	10 y
at ambient temperature < 40 °C not less than		
Property of memory	Block-by-block write protection of the user memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R112	Fujitsu MB89R112
Mechanical data	,	
Material	PA6.6 GF / brass, nickel-plated	PA6.6 GF
Color	black / silver	black
Tightening torque of the screw for securing the equipment maximum	1 Nm	-
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm
Permitted ambient conditions		
Ambient temperature		
 during read/write access 	-25 +85 °C	-25 +85 °C
 outside the read/write area 	-40 +100 °C	-40 +100 °C
 during storage 	-40 +100 °C	-40 +100 °C
Protection class IP	IP68	IP68
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²

Transponder (ISO mode)

MDS D522

Article number	6GT2600-5AF00	6GT2600-5AF00- 0AX0
Product type designation	MDS D522 transponder	MDS D522 transponder
	For gluing or screwing	For clipping
Suitability for operation	RF200	RF200
Design, dimensions and weight		
Height	6 mm	5.2 mm
Diameter	20 mm	18 mm
Net weight	13 g	1.2 g
Mounting type	gluing, screwing	Clip into the pre-milled contour according to the operating instructions
Product properties, functions, components general		
Product feature		
 silicon-free 	Yes	Yes
 printable 	No	No
Standards, specifications, approvals		
MTBF	228 у	200 у

Selection and ordering data

	Article No.
MDS D522 transponder	
For SIMATIC RF200	
8 192 byte FRAM	
Ordering quantity 10 units or a multiple thereof.	
 For attachment with glue or screws onto metal. One screw-in aid is included in each packing unit. 	6GT2600-5AF00
 for clipping onto metal 	6GT2600-5AF00-0AX0



MDS D522 transponder for clip attachment (6GT2600-5AF00-0AX0)

Transponder (ISO mode)

MDS D423

Overview



2 Kbyte METAL

The MDS D423 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can be operated with the SIMATIC RF200 and SIMATIC RF300 (ISO mode) RFID systems.

Application

The particularly compact transponder of small design can be flush-mounted in metal and is thus suitable for identifying metallic workpiece holders, workpieces or containers.

As a result of its high IP68 / IPx9K degree of protection, it is suitable for use in particularly harsh environments such as the passage through washers.

Article number	6GT2600-4AA00
Product type designation	MDS D423 transponder
Suitability for operation	BE200 BE300
Wireless frequencies	
Operating frequency Bated value	13 56 MHz
Electrical data	10.00 10112
Range maximum	80 mm:
	range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission	26.5 kbit/s
maximum Draduat facture multitagi conchia	Vec
Product realure multilag-capable	tes
	INO
memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature	1 000 000 000 000
< 40 °C maximum	1 000 000 000 000
at ambient temperature < 40 °C maximum	
Data retention time	10 y
at ambient temperature < 40 °C not less than	
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118
Mechanical data	
Material	PPS
Color	black
Tightening torque of the screw for securing the equipment maximum	1 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-25 +85 °C
 outside the read/write area 	-40 +100 °C
 during storage 	-40 +100 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	8 mm
Diameter	30 mm
Net weight	15 g
Mounting type	M4 countersunk screw
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
printable	No
Standards, specifications, approvals	
MTBF	228 у
Accessories	
Accessories	mounting hood

MDS D423

8

Selection and ordering data		Dimensional drawings
	Article No.	
MDS D423 transponder	6GT2600-4AA00	Ø 30
2 000 bytes FRAM		
Ordering quantity 10 units or a multiple thereof.		
Accessories		
Mounting cover	6GT2690-0AE00	SIEMENS N
Length = 50 mm, height = 10 mm, temperature range up to 100 $^{\circ}$ C, ordering quantity 10 units or a multiple thereof.		
Laxed inter		

MDS D423 transponder

Transponder (ISO mode)

MDS D124

Overview



-40 ℃ ATEX II 1G ATEX II 1D 300 mm ISO

The MDS D124 is a mobile, passive, maintenance-free transponder based on the ISO 15693 standard.

The MDS D124 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

This transponder can even be used problem-free under extreme environmental conditions (e.g. when subjected to temperatures up to +180 °C).

Article number	6GT2600-0AC10
Product type designation	MDS D124 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	300 mm; range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No

Article number	6GT2600-0AC10
Product type designation	MDS D124 transponder
Suitability for operation	BE200 BE300 MOBY D
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	112 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 112 bytes, configuration memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 у
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	NXP I-Code SLI
Mechanical data	
Material	PPS
Color	black
Lightening torque of the screw for securing the equipment maximum	1 Nm
Mounting distance relating to metal surfaces recommended minimum	15 mm
Permitted ambient conditions	
Ambient temperature	
during read/write access	-25 + 125 °C
outside the read/write area	-40 + 180 °C
Ambient condition for operation	-40 + 125 C
	up to 100 °C, at 180 °C: up to 5 000 hours or 3 000 temperature cycles
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	4 mm
Diameter	27 mm
Net weight	5 g
Mounting type	M3 screw, gluing
components general	
Product feature	
 silicon-free 	Yes
• printable	No
Standards, specifications, approvals	
Certificate of suitability	Ex: II 1 G Ex ia IIC T3/T6 Ga / II 1 D Ex ia IIIC T80°C/T180°C
MIBF	171 y
Accessories	Mounting oursport and an an
ACCESSOTIES	wounting support and spacer

MDS D124

Selection and ordering data		Dimensional drawings
	Article No.	
MDS D124 transponder	6GT2600-0AC10	
112 bytes EEPROM		
Ordering quantity 20 units or a multiple thereof.		
Accessories		
Mounting support and spacer	6GT2690-0AK00	
For MDS D124, MDS D324, MDS D424, MDS D524 and RF320T.		
Necessary for mounting onto metal surfaces.		
Diameter = 35 mm, height = 15 mm		
Ordering quantity 20 units or a multiple thereof.		
		MDS D124 transponder

Transponder (ISO mode)

Overview





The MDS D324 is a passive (maintenance-free) transponder based on ISO 15693.

The MDS D324 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

The MDS D324 was developed for applications in production and distribution logistics as well as product identification.

For the user, the usable application memory amounts to 992 byte.

This transponder can also be easily used in harsh environments under extreme environmental conditions (e.g. with higher thermal stress).

Article number	6GT2600-3AC00
Product type designation	MDS D224 transponder
Suitability for operation	
	RF200, RF300, MOBT D
Operating frequencies	10 50 MU
Cleatrical data	13.50 MHZ
	000 mm
Range maximum	range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission	26.5 kbit/s
maximum	20.0 101/3
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	992 byte
Type of memory organization	LIID (fixed code) 8 bytes
Type of memory organization	user memory 992 bytes,
	configuration memory 24 bytes
Number of read cycles	100 000 000 000 000
at ambient temperature	
Number of write cycles	1 000 000
at ambient temperature	1 000 000
< 40 °C maximum	
Data retention time	10 y
at ambient temperature	
Property of momeny	Plack by black write protection of
Property of memory	the user memory
Type of transponder chip used	Infineon Mv-D SRF 55V10P
Mechanical data	
Material	Epoxy resin
Color	black
Tightening torque of the screw for	1 Nm
securing the equipment maximum	
Mounting distance relating to metal	15 mm
surfaces recommended minimum	
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-25 +125 °C
 outside the read/write area 	-40 +140 °C
 during storage 	-40 +140 °C
Protection class IP	IP67
Shock resistance	According to DIN EN 60721-3-7
	Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	4 mm
Diameter	27 mm
Net weight	5 g
Mounting type	M3 screw, gluing
Product properties, functions,	
components general	
Product feature	
 silicon-free 	Yes
printable	No
Standards, specifications,	
approvals	
MTBF	171 y
Accessories	
Accessories	Mounting support and spacer

MDS D324

Selection and ordering data		Din Din	nensional	drawings	
	Article No.				
MDS D324 transponder	6GT2600-3AC00				_
992 bytes EEPROM					
Ordering quantity 20 units or a multiple thereof.					
Accessories					Щ
Mounting support and spacer	6GT2690-0AK00				
For MDS D124, MDS D324, MDS D424, MDS D524 and RF320T.				3.5	4 ± 0.2
Necessary for mounting onto metal surfaces.				27±0.2	
Diameter = 35 mm, height = 15 mm					
Ordering quantity 20 units or a multiple thereof.		MD	S D324 tran	sponder	

Transponder (ISO mode)

Overview





The MDS D424 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The MDS D424 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

The MDS D424 was developed for applications in production and distribution logistics as well as for use in assembly and production lines.

Article number	6GT2600-4AC00
Product type designation	MDS D424 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	300 mm; range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 у
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118
Mechanical data	
Material	Epoxy resin
Color	black
Tightening torque of the screw for securing the equipment maximum	1 Nm
Mounting distance relating to metal surfaces recommended minimum	15 mm
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-25 +85 °C
 outside the read/write area 	-40 +100 °C
 during storage 	-40 +100 °C
Protection class IP	IP67 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	4 mm
Diameter	27 mm
Net weight	5 g
Mounting type	M3 screw, gluing
Product properties, functions, components general	
Product feature	
 silicon-free 	Yes
printable	No
Standards, specifications, approvals	
MTBF	171 y
Accessories	
Accessories	Mounting support and spacer

MDS D424

G_KT01_XX_00173

Selection and ordering data		Dimensional drawings
	Article No.	
MDS D424 transponder	6GT2600-4AC00	
2 000 bytes FRAM		
Ordering quantity 20 units or a multiple thereof.		
Accessories		
Mounting support and spacer	6GT2690-0AK00	
For MDS D124, MDS D324, MDS D424, MDS D524 and RF320T.		
Necessary for mounting onto metal surfaces.		<u>27±0.2</u>
Diameter = 35 mm, height = 15 mm		MDS D424 transponder
Ordering quantity 20 units or a multiple thereof.		

2

Transponder (ISO mode)

Overview



·		
300 mm	8 Kbyte	ISO

The MDS D524 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can only be operated with the SIMATIC RF200 RFID system.

Application

The transponder is designed for use in production and distribution logistics as well as in assembly and production lines.

Article number	6GT2600-5AC00
	MDC D504 transponder
	RE200
	11 200
Operating frequency Bated value	
	13.30 MHz
	200
hangemaximum	range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission	26.5 kbit/s
maximum	
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	8 192 byte
Type of memory organization	UID (fixed code) 8 bytes,
	user memory 8 192 bytes,
Number of read evolop	
at ambient temperature	1 000 000 000 000
< 40 °C maximum	
Number of write cycles	1 000 000 000 000
at ambient temperature	
Data retention time	10 v
at ambient temperature	10 y
< 40 °C not less than	
Property of memory	Block-by-block write protection of
Type of transponder obje used	Life user memory
Mechanical data	
Matorial	Epoyy rosin
Color	block
Tightening torque of the screw for	1 Nm
securing the equipment maximum	
Mounting distance relating to metal	15 mm
Permitted ambient conditions	
Ambient temperature	
during read/write access	-25 +85 °C
outside the read/write area	-40 +100 °C
during storage	-40 +100 °C
Protection class IP	-40 + 100 C
Shock resistance	According to DIN EN 60721-3-7
	Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	4 mm
Diameter	27 mm
Net weight	5 g
Mounting type	M3 screw, gluing
Product properties, functions,	
components general	
Product feature	¥
	Yes
	INO
standards, specifications, approvals	
MTBF	171 v
Accessories	,
Accessories	Mounting support and spacer
	U 11

MDS D524

G_KT01_XX_00173

Selection and ordering data		Dimensional drawings
	Article No.	
MDS D524 transponder	6GT2600-5AC00	
8 192 byte FRAM		
Ordering quantity 20 units or a multiple thereof.		
Accessories		
Mounting support and spacer	6GT2690-0AK00	
For MDS D124, MDS D324, MDS D424, MDS D524 and RF320T.		
Necessary for mounting onto metal surfaces.		27±0.2
Diameter = 35 mm, height = 15 mm		MDS D524 transponder
Ordering quantity 20 units or a multiple thereof.		

Transponder (ISO mode)

MDS D425

Overview





The MDS D425 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The MDS D425 can be operated with the SIMATIC RF200 and SIMATIC RF300 (ISO mode) RFID systems.

Application

The MDS D425 is a compact and rugged ISO transponder suitable for screw mounting.

It has been designed for applications in assembly and production lines in the powertrain sector.

Article number	6GT2600-4AG00
Product type designation	MDS D425 transponder
Suitability for operation	RE200 RE300
Wireless frequencies	11 200, 11 000
Operating frequency Bated value	13.56 MHz
Electrical data	
Range maximum	45 mm; range is reader dependent: observe
http://support.automation.siemens.com	1/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission	26.5 kbit/s
maximum	
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118
Mechanical data	
Mechanical data Material	PA6.6 GF / stainless steel
Mechanical data Material Color	PA6.6 GF / stainless steel black / silver
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum	PA6.6 GF / stainless steel black / silver 6 Nm
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ²
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ²
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ²
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ²
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ²
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm 35 g
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm 35 g screwing (M6)
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product properties, functions, components general	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm 35 g screwing (M6)
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product properties, functions, components general Product feature	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm 35 g screwing (M6)
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product properties, functions, components general Product feature • silicon-free	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm 35 g screwing (M6)
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product properties, functions, components general Product feature • silicon-free • printable	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm 35 g screwing (M6)
Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product feature • silicon-free • printable Standards, specifications, approvals	PA6.6 GF / stainless steel black / silver 6 Nm 0 mm -25 +85 °C -40 + 125 °C -40 + 125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm 35 g screwing (M6) Yes No

Transponder (ISO mode)



MDS D425 transponder

Transponder (ISO mode)

MDS D525

Overview





The MDS D525 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can only be operated with the SIMATIC RF200 RFID system.

Application

The MDS D525 is a compact and rugged ISO transponder suitable for screw mounting.

It is designed for use in assembly and production lines as well as in the powertrain sector.

Article number	6GT2600-5AG00
Product type designation	MDS D525 transponder
Suitability for operation	RE200
Wireless frequencies	11 200
Operating frequency Bated value	13 56 MHz
Electrical data	
Range maximum	50 mm;
5	range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	8 192 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 8 192 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature	1 000 000 000 000
Data retention time	10 v
at ambient temperature < 40 °C not less than	
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R112
Mechanical data	
Material	PA6.6 GF / stainless steel
Color	black / silver
Color Tightening torque of the screw for securing the equipment maximum	black / silver 6 Nm
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum	black / silver 6 Nm 0 mm
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions	black / silver 6 Nm 0 mm
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature	black / silver 6 Nm 0 mm
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access	black / silver 6 Nm 0 mm -25 +85 °C
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ²
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ²
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ²
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm 35 g
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm 35 g screwing (M6)
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product properties, functions, components general	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm 35 g screwing (M6)
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product properties, functions, components general Product feature	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm 35 g screwing (M6)
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product properties, functions, components general Product feature • silicon-free	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm 35 g screwing (M6) Yes
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product properties, functions, components general Product feature • silicon-free • printable	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm 35 g screwing (M6) Yes No
Color Tightening torque of the screw for securing the equipment maximum Mounting distance relating to metal surfaces recommended minimum Permitted ambient conditions Ambient temperature • during read/write access • outside the read/write area • during storage Protection class IP Shock resistance Shock acceleration Vibrational acceleration Design, dimensions and weight Height Diameter Net weight Mounting type Product properties, functions, components general Product feature • silicon-free • printable Standards, specifications, approvals	black / silver 6 Nm 0 mm -25 +85 °C -40 +125 °C -40 +125 °C IP68 / IPx9K According to DIN EN 60721-3-7 Class 7 M3 500 m/s ² 200 m/s ² 10 mm 24 mm 35 g screwing (M6) Yes No

Transponder (ISO mode)



MDS D525 transponder

Transponder (ISO mode)

MDS D126

Overview



500 mm ISO

The MDS D126 is a passive (maintenance-free) transponder based on ISO 15693.

The MDS D126 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

The MDS D126 is a compact and rugged ISO transponder suitable for the identification of transport units in production-related logistics.

The transponder can also be used in harsh environments.

Article number	6GT2600-0AE00
Product type designation	MDS D126 transponder
	TH 200, TH 000, MODT D
Operating frequency Bated value	
	13:30 MHZ
Bango movimum	500 mm
nange maximum	range is reader dependent: observe
http://support.automation.siemens.con	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	112 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 112 bytes, configuration memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	NXP I-Code SLI
Mechanical data	
Material	PA6.6 GF
Color	black
Tightening torque of the screw for securing the equipment maximum	1 Nm
Mounting distance relating to metal surfaces recommended minimum	25 mm
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-25 +85 °C
 outside the read/write area 	-40 +100 °C
during storage	-40 +100 °C
Protection class IP	IP68
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	3.6 mm
Diameter	50 mm
Net weight	13 g
Mounting type	M4 screw
Product properties, functions, components general	
Product feature	
printable	No
Standards, specifications, approvals	
MTRE	171 v
Accessories	17 T y
Accessories	Mounting support and spacer
/ 0000001100	mounting support and space

MDS D126

	Dimensional drawings
Article No.	
6GT2600-0AE00	
6GT2690-0AL00	
	Article No. 6GT2600-0AE00 6GT2690-0AL00

MDS D126 transponder

Transponder (ISO mode)

Overview



The MDS D426 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The MDS D426 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

The MDS D426 is a compact and rugged ISO transponder suitable for the identification of transport units in production-related logistics.

The transponder can also be used in harsh environments.

Article purcher	CCT0000 441100
	6G12600-4AH00
Product type designation	MDS D426 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	400 mm;
	range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission	26.5 kbit/s
maximum	
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes,
	user memory 2 000 bytes,
	configuration memory 40 bytes
Number of read cycles	
< 40 °C maximum	
Number of write cycles	1 000 000 000 000
at ambient temperature	
< 40 °C maximum	
Data retention time	10 y
< 40 °C not less than	
Property of memory	Block-by-block write protection of
Topolly of monory	the user memory
Type of transponder chip used	Fujitsu MB89R118
Mechanical data	
Material	PA6.6 GF
Color	black
Tightening torque of the screw for	1 Nm
securing the equipment maximum	
Mounting distance relating to metal	25 mm
surfaces recommended minimum	
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-25 +85 °C
 outside the read/write area 	-40 +100 °C
 during storage 	-40 +100 °C
Protection class IP	IP68
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	3.6 mm
Diameter	50 mm
Net weight	13 a
Mounting type	M4 screw
Product properties functions	
components general	
Product feature	
printable	No
Standards, specifications.	
approvals	
MTBF	228 у
Accessories	
Accessories	Mounting support and spacer

Transponder (ISO mode)

MDS D426



MDS D426 transponder

Transponder (ISO mode)

Overview



The MDS D526 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can only be operated with the SIMATIC RF200 RFID system.

Application

The MDS D526 is a compact and rugged ISO transponder which can also be used under harsh environmental conditions.

It is designed for the identification of transport units in production-related logistics.

Article number	6GT2600-5AH00
Broduct type designation	MDS DE26 transponder
Product type designation	MDS D526 transponder
	RF200
wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	100
Range maximum	400 mm; range is reader dependent: observe
http://support automation siemens con	
Protocol with radio transmission	ISO 15693
Transfor rate with radio transmission	26 5 kbit/s
maximum	20.3 (0)(/3
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	8 192 byte
Type of memory organization	LID (fixed code) 8 bytes
Type of momery organization	user memory 8 192 bytes,
	configuration memory 40 bytes
Number of read cycles	1 000 000 000 000
at amplent temperature < 40 °C maximum	
Number of write cycles	1 000 000 000 000
at ambient temperature	
< 40 °C maximum	
Data retention time	10 y
< 40 °C not less than	
Property of memory	Block-by-block write protection of
	the user memory
Type of transponder chip used	Fujitsu MB89R112
Mechanical data	
Material	PA6.6 GF
Color	black
Tightening torque of the screw for	1 Nm
securing the equipment maximum	
Mounting distance relating to metal	25 mm
Permitted ambient conditions	
Ambient temperature	
during read/write access	-25 +85 °C
outside the read/write area	-40 +100 °C
during storage	-40 +100 °C
Protection class IP	IP68
Snock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	200
Height	3.6 mm
Diameter	50 mm
Net weight	13 a
Mounting type	M4 screw
Product properties functions	
components general	
Product feature	
printable	No
Standards, specifications, approvals	
MTBF	228 у
Accessories	,
Accessories	Mounting support and spacer
	U

Transponder (ISO mode)

MDS D526



MDS D526 transponder

Transponder (ISO mode)

MDS D117

Overview



The MDS D117 is a passive, maintenance-free transponder based on ISO 15693. It is small and compact and can be mounted on metal using adhesive.

The mobile data memory can be operated with the SIMATIC RF300 (ISO mode) and SIMATIC RF200 RFID systems. When operated with the RF350M mobile handheld terminal, an external antenna must be used.

Application

For direct identification of small metallic workpieces and workpiece holders.



Size comparison of match to MDS D117

Article number	6G12600-0AG00
Product type designation	MDS D117 transponder
Suitability for operation	RF200, RF300
wireless frequencies	
Operating frequency Rated value	13.56 MHZ
Bango movimum	4 mm
http://www.art.eutemetian.eiomana.com	a min; range is reader dependent: observe
Preteool with redia transmission	100 15002
Transfer rate with radio transmission	26.5 kbit/s
maximum	Vac
Product leature multilag-capable	No
	NO
Tupo of momony	EEDDOM
Storage especity of the user memory	112 byte
Type of memory organization	LID (fixed code) 8 bytes
type of memory organization	user memory 112 bytes, configuration memory 8 bytes
Number of read cycles	100 000 000 000 000
at ambient temperature < 40 °C maximum	
Number of write cycles	1 000 000
< 40 °C maximum	10.4
at ambient temperature < 40 °C not less than	lo y
Property of memory	Block-by-block write protection of
Type of trapeponder chip used	NYR L Code SL
Mechanical data	
Material	PPS
Color	black
Mounting distance relating to metal	0 mm
surfaces recommended minimum	
Permitted ambient conditions	
Ambient temperature	
during read/write access	-25 +85 °C
outside the read/write area	-40 +125 °C
during storage	-40 +125 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	5.2 mm
Diameter	4 mm
Net weight	1 g
Mounting type	gluing
Product properties, functions, components general	
Product feature	
• printable	No
Standards, specifications, approvals	
NATE OF	228 v

Transponder (ISO mode)



MDS D117 transponder

Transponder (ISO mode)

MDS D127

Overview





The MDS D127 is a passive, maintenance-free transponder based on ISO 15693. It is small and compact and can be screwed into metal.

The mobile data memory can only be operated with the SIMATIC RF300 (ISO mode) and SIMATIC RF200 RFID systems. When operated with the RF350M mobile handheld terminal, an external antenna must be used.

Application

For direct identification of small metallic workpieces, workpiece holders, or containers.

Article number	6GT2600-0AE00
Product type designation	MDS D127 transponder
	ni 200, ni 300
Operating frequency Bated value	13 56 MHz
Electrical data	13.30 WH 12
Bange maximum	5 mm:
hange maximum	range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission	26.5 kbit/s
maximum	¥
Product reature multitag-capable	res
Tupo of momony	EERDOM
Storage especity of the user memory	112 byte
Tupo of momony organization	LID (fixed code) 8 bytes
Type of memory organization	user memory 112 bytes, configuration memory 8 bytes
Number of read cycles	100 000 000 000 000
at ambient temperature < 40 °C maximum	
Number of write cycles	1 000 000
< 40 °C maximum	
Data retention time	10 y
at ambient temperature	
< 40 °C hot less than	Block by block write protection of
rioperty of memory	the user memory
Type of transponder chip used	NXP I-Code SLI
Mechanical data	
Material	PA6
Color	black
Mounting distance relating to metal	0 mm
Permitted ambient conditions	
Ambient temperature	
during read/write access	-25 +100 °C
outside the read/write area	-40 +125 °C
during storage	-40 +125 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7
	Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	5.8 mm
Diameter	6 mm
Net weight	1 g
Product properties functions	
components general	
Product feature	
printable	No
Standards, specifications,	
approvals	

	Article No.			
MDS 127 transponder	6GT2600-0AF00			
112 bytes EEPROM				
Ordering quantity 10 units or a multiple thereof.		-	Es10_XX_00458	

MDS D127 transponder

Transponder (ISO mode)

MDS D428

Overview



2 Kbyte METAL

The MDS D428 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The MDS D428 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

The MDS D428 is a compact and rugged ISO transponder suitable for screw mounting.

It has been designed for applications in assembly and production lines in the powertrain sector.

Article number	6GT2600-4AK00-0AX0
Product type designation	MDS D428 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	160 mm; range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	2 000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 у
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118
Mechanical data	
Material	PA6.6 GF / stainless steel
Color	black / silver
Tightening torque of the screw for securing the equipment maximum	6 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-25 +85 °C
 outside the read/write area 	-40 +125 °C
 during storage 	-40 +125 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	20 mm
Diameter	24 mm
Net weight	35 g
Mounting type	screwing (M8)
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
printable	No

M8

Transponder (ISO mode)



MDS D428 transponder

Transponder (ISO mode)

MDS D528

Overview



8 Kbyte METAL ISO

The MDS D528 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The transponder can only be operated with the SIMATIC RF200 RFID system.

Application

The MDS D528 is a compact and rugged ISO transponder suitable for screw mounting.

It is designed for use in assembly and production lines as well as in the powertrain sector.

Article number	6GT2600-5AK00
Product type designation	MDS D528 transponder
Suitability for operation	RE200
Wireless frequencies	
Operating frequency Bated value	13 56 MHz
Electrical data	10.00 10112
Range maximum	160 mm; range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	8 192 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 8 192 bytes, configuration memory 40 bytes
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 у
Property of memory	Block-by-block write protection of
Type of transponder chip used	Fujitsu MB89R112
Mechanical data	,
Material	PA6.6 GF / stainless steel
Color	black / silver
Tightening torque of the screw for securing the equipment maximum	6 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-25 +85 °C
 outside the read/write area 	-40 +125 °C
 during storage 	-40 +125 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	20 mm
Diameter	18 mm
Net weight	35 g
Mounting type	screwing (M8)
Product properties, functions,	3
components general	
Product feature	
silicon-free	Yes
printable	No

Transponder (ISO mode)



MDS D528 transponder

Transponder (ISO mode)

MDS D139

Overview





The MDS D139 is a passive (maintenance-free), heat-resistant transponder based on the ISO 15693 standard.

The MDS D139 can be used both for the MOBY D RFID system as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

Applications in production logistics and in assembly lines subject to high temperatures (up to +200 °C, e.g. in a paint shop).

Article number	6GT2600-0AA10
Product type designation	MDS D139 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	600 mm; range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No

Article number	6GT2600-0AA10
Product type designation	MDS D139 transponder
Suitability for operation	RE200 RE300 MOBY D
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	112 byte
Type of memory organization	UID (fixed code) 8 bytes,
	user memory 112 bytes,
	configuration memory 8 bytes
at ambient temperature < 40 °C maximum	
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time	10 y
at ambient temperature	
< 40 °C flot less than	Block by block write protection of
Property of memory	the user memory
Type of transponder chip used	NXP I-Code SLI
Mechanical data	
Material	PPS
Color	black
Tightening torque of the screw for	1.5 Nm
securing the equipment maximum	20
Mounting distance relating to metal surfaces recommended minimum	30 mm
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-25 +100 °C
outside the read/write area	-40 +220 °C
during storage	-40 +100 °C
Ampient condition for operation	Uperating temperature permanent up to 100 °C, at 220 °C: up to 2 000 hours or 1 500 temperature cycles, at 200 °C: up to 5 000 hours or 3 000 temperature cycles
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	15 mm
Diameter	85 mm
Net weight	50 g
Mounting type	M5 screw
Product properties, functions, components general	
Product feature	
 silicon-free 	Yes
• printable	No
Standards, specifications, approvals	
Certificate of suitability	Ex: II 3 G Ex nA II T2, II 3 D Ex tD A22 IP68 T 210°C
MIBF	228 у
Accessories	
Accessories	Spacer, quick-change holder
RFID systems for the HF range Transponder (ISO mode)

MDS D139

Selection and ordering data		Dimensional drawings		
	Article No.			
MDS D139 transponder	6GT2600-0AA10			
112 bytes EEPROM				
Ordering quantity 10 units or a multiple thereof.				
Accessories		Ø 5.5		
Spacer	6GT2690-0AA00		39	
Necessary for mounting onto metal surfaces.			000 XX	
Ordering quantity 10 units or a multiple thereof.		85	G_KT01	
•		MDS D139 transponder		
0				
Quick change holder	6GT2690-0AH00			
For MDS D139,				
stainless steel, diameter = 22 mm,				
height = 48 mm.				
Fixing with M8 nut.				
Ordering quantity 10 units or a multiple thereof.				
SIEMENS 6612690-DAHOD				
Quick change holder	6GT2690-0AH10			
For MDS D139,				
stainless steel, diameter = 22 mm				
height = 48 mm .				
With M10 female thread				
Ordering quantity 10 units or				
a multiple thereof.				
INTUENS ?				
steam of the states				
Alle Con				

2/53 Siemens ID 10 · 2016

Transponder (ISO mode)

MDS D339

Overview





The MDS D339 is a passive (maintenance-free), heat-resistant transponder based on ISO 15693.

The MDS D339 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

Applications in production logistics and in assembly lines subject to high temperatures (up to +220 °C, e.g. in a paint shop).

Technical specifications

Article number	6GT2600-3AA10
Product type designation	MDS D339 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	480 mm; range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No

Article number	6G12600-3AA10
Product type designation	MDS D339 transponder
Suitability for operation	RF200, RF300, MOBY D
Memory	FEDDOM
lype of memory	EEPROM
Storage capacity of the user memory	992 byte
Type of memory organization	UID (fixed code) 8 bytes,
	configuration memory 24 bytes
Number of read cycles	100 000 000 000 000
at ambient temperature	
Number of write cycles	1 000 000
at ambient temperature	
< 40 °C maximum	
Data retention time	10 y
< 40 °C not less than	
Property of memory	Block-by-block write protection of
	the user memory
lype of transponder chip used	Infineon My-D SRF 55V10P
Mechanical data	DDC
Material	PPS
Color Tightoning targue of the agroup for	
securing the equipment maximum	1.5 MI
Mounting distance relating to metal	30 mm
surfaces recommended minimum	
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-25 +100 °C
 outside the read/write area 	-40 +220 °C
during storage	-40 +100 °C
Ambient condition for operation	Operating temperature permanent
	at 220 °C: up to 2 000 hours or
	1 500 temperature cycles,
	3 000 temperature cycles
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7
	Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s²
Height	15 mm
Diameter	85 mm
Net weight	50 a
Mounting type	M5 screw
Product properties. functions.	
components general	
Product feature	
• silicon-free	Yes
printable	No
standards, specifications, approvals	
Certificate of suitability	Ex:
-	II 3 G Ex nA II T2,
MTRE	
	220 y
Accessories	Spacer quick-change holder
///////////////////////////////////////	opacer, quier enange noider

RFID systems for the HF range Transponder (ISO mode)

MDS D339

Selection and ordering data		Dimensional drawings	
	Article No.		
MDS D339 transponder	6GT2600-3AA10	\frown \Box	
992 bytes EEPROM			
Ordering quantity 10 units or a multiple thereof.			
Accessories		Ø 5.5 0 5.5	
Spacer	6GT2690-0AA00		39
Necessary for mounting onto metal surfaces.			000 XX 1
Ordering quantity 10 units or a multiple thereof.		85	G_KT0
•		MDS D220 transponder	
		MD2 D229 (ransponder	
Quick change holder	6GT2690-0AH00		
For MDS D339, stainless steel.			
diameter = 22 mm,			
Fixing with M8 nut			
Ordering quantity 10 units or a multiple thereof.			
SIEMENS 6GI2690-0AH00			
Quick change holder	6GT2690-0AH10		
For MDS D339,			
diameter = 22 mm,			
height = 48 mm.			
With M10 female thread			
multiple thereof			
1015			
SIEMEN SIEMEN			
Alle Color			

Transponder (ISO mode)

MDS D160

Overview



-40 °C ISO

The MDS D160 is a passive, maintenance-free and rugged transponder based on the ISO 15693 standard.

The MDS D160 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

Typical applications are, for example:

- Rented work clothing
- Hotel laundry
- Surgical textiles
- Hospital clothing
- Dirt collection mats
- Clothing for nursing homes/hostels

Technical specifications

Article number	6GT2600-0AB10
Product type designation	MDS D160 transponder
Suitability for operation	RF200, RF300, MOBY D
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	180 mm; range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No

Article number	6GT2600-0AB10	
Product type designation	MDS D160 transponder	
Suitability for operation	RF200, RF300, MOBY D	
Memory		
Type of memory	EEPROM	
Storage capacity of the user memory	112 byte	
Type of memory organization	UID (fixed code) 8 bytes, user memory 112 bytes, configuration memory 8 bytes	
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000	
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000	
Data retention time at ambient temperature < 40 °C not less than	10 у	
Property of memory	Block-by-block write protection of the user memory	
Type of transponder chip used	NXP I-Code SLI	
Mechanical data		
Material	PPS	
Color	beige	
Mounting distance relating to metal surfaces recommended minimum	10 mm	
Permitted ambient conditions		
Ambient temperature		
 during read/write access 	-25 +85 °C	
 outside the read/write area 	-40 +175 °C	
 during storage 	-25 +100 °C	
Ambient condition for operation	Operating temperature permanent up to 100 °C, up to 175 °C min. 100 washing cycles, one time up to 220 °C for 30 s	
Protection class IP	IP68 / IPx9K	
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	
Shock acceleration	400 m/s ²	
Vibrational acceleration	100 m/s ²	
Design, dimensions and weight		
Height	3 mm	
Diameter	16 mm	
Net weight	1.2 g	
Mounting type	patch, sewing, gluing	
Product properties, functions, components general		
Product feature		
printable	No	
Standards, specifications, approvals		
MTBF	228 у	
Accessories		
Accessories	Mounting support and spacer	

RFID systems for the HF range Transponder (ISO mode)

Selection and ordering data		Dimensional drawings	
	Article No.		
MDS D160 transponder	6GT2600-0AB10		
112 bytes EEPROM			
Ordering quantity 100 units or a multiple thereof.			
Accessories			0026
Spacer for MDS D160	6GT2690-0AG00		G_KT01_XX_0
For MDS D160, necessary for mounting onto metal surfaces. Diameter = 20 mm, height = 15 mm.		$\varphi = 0$ 16 \rightarrow $\varphi = 0$ $\varphi = 0$	
Ordering quantity 50 units or a multiple thereof.			
		MDS D160 transponder	
IC.			

Transponder (ISO mode)

MDS D460

Overview





The MDS D460 is a passive (maintenance-free) transponder based on ISO 15693, with FRAM technology.

The MDS D460 can be used for the RFID system MOBY D as well as for SIMATIC RF200 and SIMATIC RF300 (ISO mode).

Application

The MDS D460 has been designed for identification tasks in small assembly lines.

Technical specifications

Article number	6GT2600-4AB00	
Product type designation	MDS D460 transponder	
Suitability for operation	RE200, RE300, MOBY D	
Wireless frequencies		
Operating frequency Bated value	13 56 MHz	
Electrical data		
Range maximum	160 mm; range is reader dependent: observe	
http://support.automation.siemens.com	n/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693	
Transfer rate with radio transmission maximum	26.5 kbit/s	
Product feature multitag-capable	Yes	
Product component Backup battery	No	
Memory		
Type of memory	FRAM	
Storage capacity of the user memory	2 000 byte	
Type of memory organization	UID (fixed code) 8 bytes, user memory 2 000 bytes, configuration memory 40 bytes	
Number of read cycles at ambient temperature < 40 °C maximum	1 000 000 000 000	
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000 000 000	
Data retention time at ambient temperature < 40 °C not less than	10 у	
Property of memory	Block-by-block write protection of the user memory	
Type of transponder chip used	Fujitsu MB89R118	
Mechanical data		
Material	Epoxy resin	
Color	black	
Mounting distance relating to metal surfaces recommended minimum	10 mm	
Permitted ambient conditions		
Ambient temperature		
 during read/write access 	-25 +85 °C	
 outside the read/write area 	-40 +100 °C	
 during storage 	-40 +100 °C	
Protection class IP	IP67 / IPx9K	
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	
Shock acceleration	500 m/s²	
Vibrational acceleration	200 m/s ²	
Design, dimensions and weight		
Height	3 mm	
Diameter	16 mm	
Net weight	3 g	
Mounting type	patching, gluing	
Product properties, functions, components general		
Product feature		
• printable	No	
Standards, specifications, approvals		
MTBF	228 у	
Accessories		
Accessories	Mounting support and spacer	

RFID systems for the HF range Transponder (ISO mode)

Selection and ordering data		Dimensional drawings	
	Article No.		
MDS D460 transponder	6GT2600-4AB00		
2 000 bytes FRAM			
Ordering quantity 50 units or a multiple thereof.			
Accessories			0026
Spacer	6GT2690-0AG00		Ň
For MDS D460, necessary for mounting onto metal surfaces.			G_KT01_
Diameter = 20 mm, height = 15 mm			
Ordering quantity 50 units or a multiple thereof.			
		MDS D460 transponder	

Transponder (RF300 mode)

Introduction

Overview

The following RF300 mode transponders can be used with the SIMATIC RF300 RFID system:

Transponder	Features	Page	Transponder	Features	Page
RF320T	Small, compact, universal transponder. 20 byte EEPROM	2/61	RF370T	Universal transponder with 32 KB or 64 KB memory, for mounting directly on metal, suitable for longer ranges.	2/71
RF330T	Transponder, can be directly flush-mounted on metal. For directly identifying metallic workpieces or containers. 32 KB FRAM	2/63	RF380T	Heat-resistant transponder, designed for skid identification in paint shops, for mounting directly on metal. Temperature range to +220 °C. 32 KB FRAM	2/73
RF340T	Universal transponder, for mounting directly on metal, e.g. workpiece	2/65			
STEPART, B SIMATIC RF340T GGT2000-4000	holders. 8 or 32 KB FBAM		Benefits		
			g Get	Designed for Indus	try nders
			 For high-performa 	ance applications.	011.
RF350T SIEMENS SIMATIC PE350T	Universal transponder, for mounting directly on metal, suitable for longer ranges. 32 KB FRAM	2/67	 Large memory up IP68 / IPx9K degree Extremely rugged up to 220 degrees Customized soluti 	to 64 KB. ee of protection. transponder for high temperature ra s with ATEX approval for use in paint ons for Smartl abels and transponde	anges shops.
			request.		
66T2800-58000 AS A			Technical specifica	itions	
			Field data (operatir readers (all specific	ng/limit distance) of transponders cations in mm)	and
RF360T SIEMENS	Universal transponder in credit card format. For mounting onto metal with spacer. 8 or 32 KB FRAM	2/69	The field data (unaff in connection with R ifications of the RFID typical values and a	ected by metal) of the RF300 transp F300 readers is listed in the technic o overview. The listed technical data re valid for a room temperature of +2	onders al spec- are 25 °C.
RF360T est72800-44.cop			For detailed descrip transponders: Refer	tions and ordering data of these RF3 to the following product nodes.	300

RFID systems for the HF range

Transponder (RF300 mode)

RF320T

Overview



140 ∕°C 1 40 ℃ **RF300**

Technical specifications

Article number	6GT2800-1CA00
Product type designation	RF320T transponder
Suitability for operation	RF300
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	60 mm; range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	RF300-specific
Transfer rate with radio transmission maximum	106 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	20 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 20 bytes,
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	1 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Mechanical data	
Material	Epoxy resin
Color	black
Mounting distance relating to metal surfaces recommended minimum	20 mm

Article number	6GT2800-1CA00
Product type designation	RF320T transponder
Suitability for operation	RF300
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-25 +125 °C
 outside the read/write area 	-40 +140 °C
 during storage 	-40 +140 °C
Protection class IP	IP67 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	4 mm
Diameter	27 mm
Net weight	5 g
Mounting type	M3 screw, gluing
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
printable	No
Standards, specifications, approvals	
MTBF	1 800 y
Accessories	
Accessories	Mounting support and spacer

Universal, compact transponder (20 bytes EEPROM + 4 bytes serial number) in button format. Dimensions \emptyset x H (mm): 27 x 4.

Transponder (RF300 mode)

RF320T

Selection and ordering data

Dimensional drawings





SIMATIC RF320T transponder

Transponder (RF300 mode)

RF330T

2



The SIMATIC RF330T is a universal transponder. This compact transponder can be flush-mounted in and on metal. It is thus suitable for directly identifying metallic workpiece holders, workpieces or containers. Thanks to its high IP68/IPx9K degree of protection, it is suitable for use in particularly harsh environments such as the passage through washers.

Technical specifications

Article number	6GT2800-5BA00
Product type designation	RF330T transponder
Suitability for operation	RF300
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	52 mm; range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	RF300-specific
Transfer rate with radio transmission maximum	106 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM/EEPROM
Storage capacity of the user memory	32 765 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 32 765 bytes, OTP memory 20 bytes
Number of read cycles at ambient temperature < 40 °C maximum	10 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	10 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the OTP memory

Article number	6GT2800-5BA00
Product type designation	RF330T transponder
Suitability for operation	RF300
Mechanical data	
Material	PPS
Color	black
Tightening torque of the screw for securing the equipment maximum	1.2 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-25 +85 °C
 outside the read/write area 	-40 +100 °C
 during storage 	-40 +100 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Height	8 mm
Diameter	30 mm
Net weight	15 g
Mounting type	M4 countersunk screw
Product properties, functions, components general	
Product feature	
silicon-free	Yes
printable	No
Standards, specifications, approvals	
MTBF	1 200 y
Accessories	
Accessories	mounting hood

RFID systems for the HF range Transponder (RF300 mode)

RF330T

Selection and ordering data		Dimensional drawings
	Article No.	
SIMATIC RF330T transponder	6GT2800-5BA00	
32 KB FRAM		
Ordering quantity 10 units or a multiple thereof.		Ø4
Accessories		66T280Q-5BA00
Mounting cover	6GT2690-0AE00	
Length = 50 mm, height = 10 mm, temperature range up to 100 °C, ordering quantity 10 units or a multiple thereof.		RFSOUT
		30 →

SIMATIC RF330T transponder

G_FS10_XX_01144 8

RF340T

SIEMENS B SIEMENS B SIMATIC RF 340 T 6GT2800-4BB00 GGT2800-4BB00 GGT2800-4BB00 GGT2800-4BB00 GGT2800-4BB00 GGT2800-4BB00 GGT2800-5BB00 GGT2800-5BB00 GGT2800-5BB00

Technical specifications

Overview

Article number	6GT2800-4BB00	6GT2800-5BB00
Product type designation	RF340T transponder	RF340T transponder
Suitability for operation	RF300	RF300
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	105 mm; range is reader dependent: observe http://suppor	t.automation.siemens.com/WW/view/en/67384964
Protocol with radio transmission	RF300-specific	RF300-specific
Transfer rate with radio transmission maximum	106 kbit/s	106 kbit/s
Product feature multitag-capable	Yes	Yes
Product component Backup battery	No	No
Memory		
Type of memory	FRAM/EEPROM	FRAM/EEPROM
Storage capacity of the user memory	8 189 byte	32 765 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 8 189 bytes, OTP memory 20 bytes	UID (fixed code) 4 bytes, user memory 32 765 bytes, OTP memory 20 bytes
Number of read cycles at ambient temperature < 40 °C maximum	10 000 000 000	10 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	10 000 000 000	10 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y	10 y
Property of memory	Block-by-block write protection of the OTP memory	Block-by-block write protection of the OTP memory

Universal transponder, especially suitable for small workpiece holders. The transponder can be mounted directly onto metal surfaces.

Transponder (RF300 mode)

RF340T

Article number	6GT2800-4BB00	6GT2800-5BB00
Product type designation	BE340T transponder	BE340T transponder
Suitability for operation	RE300	RE300
Mechanical data	11 300	11 500
Material	PΔ12	ΡΔ12
Color	anthracite	anthracite
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm
Permitted ambient conditions		
Ambient temperature		
 during read/write access 	-25 +85 °C	-25 +85 °C
 outside the read/write area 	-40 +85 °C	-40 +85 °C
 during storage 	-40 +85 °C	-40 +85 °C
Protection class IP	IP67 / IPx9K	IP67 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Width	25 mm	25 mm
Height	15 mm	15 mm
Depth	48 mm	48 mm
Net weight	25 g	25 g
Mounting type	2 x M3 screws	2 x M3 screws
Product properties, functions, components general		
Product feature		
silicon-free	Yes	Yes
printable	No	No
Standards, specifications, approvals		
MTBF	1 200 y	1 200 y

Selection and ordering data

Article No.SIMATIC RF340T transponder• 8 KB FRAM
Ordering quantity 5 units or a
multiple thereof.• 32 KB FRAM
Order quantity 5 units or a
multiple thereof.6GT2800-5BB00





SIMATIC RF340T transponder

2

Transponder (RF300 mode)

RF350T



Universal transponder. The transponder can be mounted directly onto metal surfaces.

RF300

Speed

Technical specifications

METAL

32 Kbyte

Article number	6GT2800-5BD00
Product type designation	RF350T transponder
Suitability for operation	RF300
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	125 mm; range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	RF300-specific
Transfer rate with radio transmission maximum	106 kbit/s
Product feature multitag-capable	Yes
Product component Backup battery	No
Memory	
Type of memory	FRAM/EEPROM
Storage capacity of the user memory	32 765 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 32 765 bytes, OTP memory 20 bytes
Number of read cycles at ambient temperature < 40 °C maximum	10 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	10 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	Block-by-block write protection of the OTP memory

Article number	6GT2800-5BD00
Product type designation	RF350T transponder
Suitability for operation	RF300
Mechanical data	
Material	PA12
Color	anthracite
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-25 +85 °C
 outside the read/write area 	-40 +85 °C
 during storage 	-40 +85 °C
Protection class IP	IP68
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Width	50 mm
Height	20 mm
Depth	50 mm
Net weight	25 g
Mounting type	2 x M4 screws
Product properties, functions, components general	
Product feature	
silicon-free	Yes
printable	No
Standards, specifications, approvals	
MTBF	1 200 у

Selection and ordering data

SIMATIC RF350T transponder
32 Kbyte FRAM

Article No. 6GT2800-5BD00

Transponder (RF300 mode)

RF350T

Dimensional drawings



Left: Transponder SIMATIC RF350T. Top right: Mounting frame. Lower right: Installation diagram. The transponder can be mounted with the mounting frame as shown.

RF360T



Technical specifications

Article number	6GT2800-4AC00	6GT2800-5AC00
Product type designation	RF360T transponder	RF360T transponder
Suitability for operation	RF300	RF300
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	150 mm; range is reader dependent: observe http://suppor	t.automation.siemens.com/WW/view/en/67384964
Protocol with radio transmission	RF300-specific	RF300-specific
Transfer rate with radio transmission maximum	106 kbit/s	106 kbit/s
Product feature multitag-capable	Yes	Yes
Product component Backup battery	No	No
Memory		
Type of memory	FRAM/EEPROM	FRAM/EEPROM
Storage capacity of the user memory	8 189 byte	32 765 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 8 189 bytes, OTP memory 20 bytes	UID (fixed code) 4 bytes, user memory 32 765 bytes, OTP memory 20 bytes
Number of read cycles at ambient temperature < 40 °C maximum	10 000 000 000	10 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	10 000 000 000	10 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y	10 y
Property of memory	Block-by-block write protection of the OTP memory	Block-by-block write protection of the OTP memory
Mechanical data		
Material	Epoxy resin	Epoxy resin
Color	anthracite	anthracite
Mounting distance relating to metal surfaces recommended minimum	20 mm	20 mm

Universal transponder in credit card format. The transponder can be mounted on metal with spacers.

Transponder (RF300 mode)

RF360T

Article number	6GT2800-4AC00	6GT2800-5AC00
Product type designation	RF360T transponder	RF360T transponder
Suitability for operation	RF300	RF300
Permitted ambient conditions		
Ambient temperature		
 during read/write access 	-25 +75 °C	-25 +75 °C
 outside the read/write area 	-40 +85 °C	-40 +85 °C
 during storage 	-40 +85 °C	-40 +85 °C
Protection class IP	IP67	IP67
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Resistance to mechanical stress	Continuous torsion and bending stress not permissible	Continuous torsion and bending stress not permissible
Design, dimensions and weight		
Width	55 mm	55 mm
Height	2.5 mm	2.5 mm
Depth	86 mm	86 mm
Net weight	25 g	25 g
Mounting type	2 x M3 screws, mounting bag (see accessories)	2 x M3 screws, mounting bag (see accessories)
Product properties, functions, components general		
Product feature		
• silicon-free	Yes	Yes
printable	No	No
Standards, specifications, approvals		
MTBF	1 200 y	1 200 у
Accessories	Fixing strap, holder	Fixing strap, holder

Selection and ordering data

	Article No.
SIMATIC RF360T transponder	
 8 Kbyte FRAM Ordering quantity 10 units or a multiple thereof. 	6GT2800-4AC00
 32 Kbyte FRAM Ordering quantity 10 units or a multiple thereof. 	6GT2800-5AC00
Accessories	
Fixing pocket	6GT2190-0AB00
For SIMATIC RF360T, only usable together with spacer 6GT2190-0AA00.	
Ordering quantity 50 units or a multiple thereof.	
Spacer	6GT2190-0AA00
For fixing pocket (6GT2190-0AB00), thickness 20 mm.	
The purpose of the spacer is to main- tain the recommended distance to the metal when installing the transponder.	
Ordering quantity 50 units or a multiple thereof.	





SIMATIC RF360T transponder

Dimensional drawings

RF370T



Technical specifications

Article number	6GT2800-5BE00	6GT2800-6BE00
Product type designation	RF370T transponder	RF370T transponder
Suitability for operation	RF300	RF300
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	135 mm; range is reader dependent: observe http://suppor	t.automation.siemens.com/WW/view/en/67384964
Protocol with radio transmission	RF300-specific	RF300-specific
Transfer rate with radio transmission maximum	106 kbit/s	106 kbit/s
Product feature multitag-capable	Yes	Yes
Product component Backup battery	No	No
Memory		
Type of memory	FRAM/EEPROM	FRAM/EEPROM
Storage capacity of the user memory	32 765 byte	65 277 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 32 765 bytes, OTP memory 20 bytes	UID (fixed code) 4 bytes, user memory 65 277 bytes, OTP memory 20 bytes
Number of read cycles at ambient temperature < 40 °C maximum	10 000 000 000	10 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	10 000 000 000	10 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y	10 y
Property of memory	Block-by-block write protection of the OTP memory	Block-by-block write protection of the OTP memory

Transponder (RF300 mode)

RF370T		
Article number	6GT2800-5BE00	6GT2800-6BE00
Product type designation	RF370T transponder	RF370T transponder
Suitability for operation	RF300	RF300
Mechanical data		
Material	PA12	PA12
Color	anthracite	anthracite
Tightening torque of the screw for securing the equipment maximum	1.2 Nm	1.2 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm
Permitted ambient conditions		
Ambient temperature		
 during read/write access 	-25 +85 °C	-25 +85 °C
 outside the read/write area 	-40 +85 °C	-40 +85 °C
 during storage 	-40 +85 °C	-40 +85 °C
Protection class IP	IP68	IP68
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Width	75 mm	75 mm
Height	41 mm	41 mm
Depth	75 mm	75 mm
Net weight	200 g	200 g
Mounting type	2 x M5 screws	2 x M5 screws
Product properties, functions, components general		
Product feature		
 silicon-free 	Yes	Yes
printable	No	No
Standards, specifications, approvals		
MTBF	1 200 у	1 200 у

Selection and ordering data

 Article No.

 SIMATIC RF370T transponder

 • 32 KB FRAM

 • 64 KB FRAM

 • 6GT2800-5BE00

Dimensional drawings





G_FS10_XX_00237



SIMATIC RF370T transponder

RF<u>380T</u>



Heat-resistant transponder, designed for skid identification in paint shops, temperature range up to +220 $^\circ C$ (cyclic).

Mode of operation

Cyclic operation of the transponder at temperatures > 100 °C

At ambient temperatures between +110 °C and +220 °C, care must be taken to ensure that the internal temperature of the SIMATIC RF380T does not exceed the critical threshold of +110 °C. Each heating phase must therefore be followed by a cooling phase. Some limit cycles are listed in the table below.

Heating up		Cooling down	Cooling down	
Temperature	Time	Temperature	Time	
200 °C	2 h	25 °C	> 8 h	
200 °C	1 h	25 °C	> 2 h	
190 °C	2 h	25 °C	> 7 h	
190 °C	1 h	25 °C	> 1 h 45 min	
180 °C	2 h	25 °C	> 5 h 30 min	
180 °C	2 h	25 °C	> 4 h 30 min	

A temperature calculation tool computes the temperature curve for the heat-proof SIMATIC RF380T transponder (see DVD "RFID Systems Software & Documentation", Article No. 6GT2080-2AA20).

Application

Typical applications are:

- Primer application, cataphoresis with the associated drying ovens
- Outer paint coating area with drying ovens
- Washing area with temperatures > $+85^{\circ}C$

RFID systems for the HF range Transponder (RF300 mode)

RF380T

Technical specifications

Article number	6GT2800-5DA00	
Product type designation	RF380T transponder	
Suitability for operation	RF300	
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	
Electrical data		
Range maximum	160 mm; range is reader dependent: observe	
http://support.automation.siemens.com	m/WW/view/en/67384964	
Protocol with radio transmission	RF300-specific	
Transfer rate with radio transmission maximum	106 kbit/s	
Product feature multitag-capable	Yes	
Product component Backup battery	No	
Memory		
Type of memory	FRAM/EEPROM	
Storage capacity of the user memory	32 765 byte	
Type of memory organization	UID (fixed code) 4 bytes, memory 32 765 bytes, OTP memory 20 bytes	
Number of read cycles	10 000 000 000	
at ambient temperature < 40 °C maximum		
Number of write cycles at ambient temperature < 40 °C maximum	10 000 000 000	
Data retention time at ambient temperature < 40 °C not less than	10 у	
Property of memory	Block-by-block write protection of the OTP memory	
Mechanical data		
Material	PPS	
Color	brown	
Mounting distance relating to metal surfaces recommended minimum	0 mm	
Permitted ambient conditions		
Ambient temperature		
 during read/write access 	-25 +110 °C	
 outside the read/write area 	-40 +220 °C	
 during storage 	-40 +110 °C	
Ambient condition for operation	Cyclic operation at ambient temperature >110 °C	
Protection class IP	IP68	
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	
Shock acceleration	500 m/s ²	
Vibrational acceleration	200 m/s ²	
Design, dimensions and weight	20	
Height	83 mm	
Diameter	114 mm	
Net weight	900 g	
Mounting type	mount (see accessories)	
Product properties, functions, components general		
	¥	
	res	
printable Standards specifications	INO	
approvals		
MTRE	1 200 v	
	1 200 y	
Accessories	Skid holder, shrouding cover, universal holder	

Selection and ordering data

	Article No.
Transponder SIMATIC RF380T	6GT2800-5DA00
With 32 KB FRAM	
Accessories	
Skid support for SIMATIC RF380T	6GT2090-0QA00
Short type	
Universal support	6GT2590-0QA00
For SIMATIC RF380T, e.g. for attaching to the body.	
Shrouding cover	6GT2090-0QB00
For skid support.	

Transponder (RF300 mode)

RF380T

Dimensional drawings



SIMATIC RF380T transponder



Skid holder for RF380T



Skid holder, shrouding cover for RF380T



Universal holder for RF380T

RFID systems for the HF range SIMATIC RF200

Overview



The RFID system SIMATIC RF200 is, thanks to its compact and low-cost reader, particularly suitable for use in industrial production in the areas of small assembly lines and intralogistics.

With RF200, identification tasks of medium-performance in the RF range (13.56 MHz, ISO 15693) can be implemented extremely cost effectively. RF200 readers can be operated with all ISO transponders.

The communication modules that can be used for all MOBY and SIMATIC RF systems (ASM 456, ASM 475, SIMATIC RF1xxC) are available for connecting to SIMATIC S7, PROFIBUS, PROFINET, Ethernet/IP and TCP/IP (XML).

IO-Link

For simple identification tasks (e.g. reading an identification number) the RF210R/RF220R//RF240R/RF250R/RF260R readers are available in an interface version for IO-Link. With the help of this standardized interface it is extremely easy and economical to integrate the data automatically read by the reader into the automation level. The SIMATIC RF200 readers can be connected to the controllers of many well-known suppliers of automation solutions through an appropriate IO-Link master module.

Siemens offers IO-Link master modules for S7-1200, ET 200S, ET 200SP, ET 200AL and ET 200eco PN In this way, IO-Link is seamlessly integrated into the established PROFINET and PROFIBUS field buses and into the world of Totally Integrated Automation (TIA Portal).

The Siemens master modules allow up to four SIMATIC RF200 IO-Link readers to be connected.

The essential features of IO-Link are:

- Ease of use: No RFID-specific programming is necessary, ideal for RFID beginners.
- Particularly low channel costs per reading point (reader + IO-Link master interface).
- Openness through standardization: Many well-known manufacturers offer IO-Link masters.

The SIMATIC RF200 identification system offers the following features:

- 13.56 MHz operating frequency (operation according to ISO 15693).
- Passive (without battery), maintenance-free transponders (MDS Dxxx) with memory capacities up to 8 KB FRAM.
- Rugged, compact components with IP67 degree of protection.
- Easy integration into SIMATIC, PROFIBUS, PROFINET and TCP/IP.
- Reader versions with RS422, RS232 or IO-Link.

Benefits

G Get Designed for Industry

- · Price-optimized and compact, space-saving components.
- Operation with the attractively priced and battery-free ISO 15693 transponders for low investment and operating costs.
- Flexible and economic solutions thanks to the complete and scalable portfolio for the field of industrial identification.
- Simplified engineering, commissioning, diagnostics and maintenance through seamless integration into Totally Integrated Automation:
- Integrated bus connection to an automation system, such as SIMATIC, SIMOTION or SINUMERIK via communication modules with PROFIBUS and PROFINET.
- Simple S7 software integration via ready-to-use function blocks.
- High investment security thanks to:
 - Open ISO 15693 standard.
 - Software compatibility between the RFID systems of Siemens.
- Standardized communication interfaces.
- Openness through connection options to various bus systems from different manufacturers and PC environments via communication modules, RS232 or IO-Link.
- Worldwide Service and Support.
- tionsmodule, RS232 oder IO-Link.
- Weltweiter Service und Support.

Application

The RFID system SIMATIC RF200 is primarily used for noncontact identification of containers, pallets and workpiece holders where the demands on performance (data transmission rate, memory volume) satisfy the ISO 15693 standard.

The main application areas for SIMATIC RF200 are:

- Assembly and handling systems, assembly lines (identification of workpiece carriers), especially small assembly lines.
- Production logistics (material flow control, identification of containers and other vessels), intralogistics.
- Parts identification (the transponder is attached to the products or pallets).
- Conveyor systems (e.g. suspended monorail).

Introduction

Design

Due to their compact design and the integrated antenna, SIMATIC RF200 readers are suitable for mounting in confined spaces, e.g. in small assembly lines or in intralogistics.

The high IP67 degree of protection of the SIMATIC RF200 reader enables it to be used in harsh industrial environments.

Each SIMATIC RF200 reader has a multicolor LED which indicates the function and status of the reader on-site, as well as the presence of a transponder.

The interface to the automation level can be implemented by means of communication modules. For quick and easy cabling, pre-assembled cables with M12 plug-in connectors are available in various lengths.

Transponders compliant with ISO 15693 are used as mobile data carriers.

Transponders suitable for a wide variety of different requirements can be selected from an extensive range: For example, low-cost SmartLabels in rugged credit card format, or screw-fit transponders that can be attached by robots.

The transponders are attached to the object to be identified, e.g. by means of screws, adhesive or pre-assembled spacer.

Function

All of the SIMATIC RF200 readers are suitable for reliable reading and writing tasks in the HF range of 13.56 MHz. The SIMATIC RF200 IO-Link readers are designed for simple identification tasks.

The readers are connected (via an RS422 interface) to the automation level (e.g. SIMATIC S7) by means of communication modules over standard fieldbuses (e.g. PROFIBUS or PROFINET).

User-friendly function blocks are available for the S7 programming.

In the event of an error, the S7 application receives a detailed error message from the communication module via the function block.

In addition, there are the SIMATIC RF240R, RF250R and RF260R readers with an RS232 interface for connection to to the PC or to SIMATIC S7-1200.

The SIMATIC RF210R, RF220R, RF240R, RF250R and RF260R readers are available as versions with IO-Link interface.

Integration

A wide range of communication modules, function blocks, as well as high-performance drivers and function libraries permits easy and quick integration into the application.

And best of all: SIMATIC RF200 is part of Totally Integrated Automation (TIA) and can be integrated easily and cost-effectively into the SIMATIC world.

The IO-Link versions of the RF200 readers are integrated into the control level with the help of standardized IO-Link masters.

For more details on the connection possibilities, see Chapter 5 "Communication Modules".

SIMATIC Ident Configuration Guide

Here is a compact configuration tool for setting up RFID systems:

http://support.automation.siemens.com/WW/view/en/67384964

Technical specifications

RFID system	SIMATIC RF200
Transmission frequency	13.56 MHz
Maximum range	650 mm
Protocol (air interface)	• ISO 15693
	• ISO 18000-3
Approvals ¹⁾	• EN 300330, 301489, CE
	FCC Part 15
	• UL/CSA
Memory capacity	max. 992 bytes (EEPROM) / 8 192 bytes (FRAM)
Data transfer rate, reader – transponder (not for IO-Link)	
Read	Max. 1.5 kbyte/s
Write	Max. 1.5 kbyte/s
Transmission time per byte for user data (IO-Link versions)	Typ. 40 ms
Multitag/Bulk capability	With RF290R reader only
Special features	 Particularly compact designs For particularly low-cost RFID solutions IO-Link for simple identification tasks

 All current wireless approvals can be found on the Internet at: http://www.siemens.com/rfid-approvals

RFID systems for the HF range SIMATIC RF200 readers

Introduction

Readers	Feature	Page	Readers	Feature	Page
RF210R	M18 reader with integrated antenna.	2/79	RF250R	Extremely small compact reader for connecting external antennas (ANT 3, 8, 12, 18 and 30).	2/90
RF210M	Handheld reader with integrated RF210R reader.	2/82	RF260R	Compact reader with integrated antenna.	2/95
RF220R	M30 reader with integrated antenna.	2/83	RF290R	High-performance reader for connecting external antennas (ANT D5, D6, D10).	2/99
RF240R	Very small compact reader with integrated antenna	2/86	RF350M	Handheld terminal with integrated or external read/write antenna.	2/117

RF210R

Overview



CM ISO

6GT2821-1AC32

Design

O IO-Link

Minimum distance from reader to reader

ISO

SIMATIC RF210R

Technical specifications

Article number	6GT2821-1AC10	6GT2821-1AC32
Product type designation	RF210R reader	RF210R reader IO-Link
Suitability for operation	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	ISO 15693 transponders (MDS Dxxx), for connecting to an IO-Link master
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	20 mm; Range is dependent on transponder type: observe h	ttp://support.automation.siemens.com/WW/view/en/67384964
Protocol with radio transmission	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	No	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	38.4 kbit/s
Transmission time for user data		
 for write access per byte typical 	0.6 ms	40 ms
 for read access per byte typical 	0.6 ms	40 ms
Interfaces		
Standard for interfaces for communication	RS422	IO-Link
Type of electrical connection	M12, 8-pin	M12, 4-pin
Mechanical data		
Material	Brass, nickel-plated / PBT	Brass, nickel-plated / PBT
Color	silver/pastel turquoise	silver/pastel turquoise
Tightening torque of the screw for securing the equipment maximum	20 Nm	20 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm

≥ 100 mm

SIMATIC RF210R is an M18 reader with integrated antenna. Its extremely compact design makes it ideal for use on small assembly lines.

This reader has either

- an RS422 interface with 3964R transmission procedure for connection to RFID communication modules (see Chapter 5),
- or a standardized IO-Link interface for connection to IO-Link master modules from Siemens or third parties.

Thanks to its high degree of protection and rugged design, the SIMATIC RF210R reader enables problem-free use even under the toughest industrial conditions. Connection is by means of either an 8-pin M12 plug-in connector (RS422 version) or a 4-pin M12 plug-in connector (IO-Link version).

The reader is operated with ISO 15693-compatible transponders.

RFID systems for the HF range SIMATIC RF200 readers

RF210R

Article number	6GT2821-1AC10	6GT2821-1AC32	
Product type designation	RF210R reader	RF210R reader IO-Link	
Supply voltage, current consumption, power loss			
Supply voltage			
 at DC Rated value 	24 V	24 V	
• at DC	20.4 28.8 V	20.4 28.8 V	
Consumed current at 24 V DC			
typical	0.05 A	0.05 A	
Permitted ambient conditions			
Ambient temperature			
 during operation 	-20 +70 °C	-20 +70 °C	
 during storage 	-25 +80 °C	-25 +80 °C	
 during transport 	-25 +80 °C	-25 +80 °C	
Protection class IP	IP67	IP67	
Shock resistance	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2	
Shock acceleration	500 m/s ²	500 m/s ²	
Vibrational acceleration	200 m/s ²	200 m/s ²	
Design, dimensions and weight			
Height	83 mm	83 mm	
Diameter	18 mm	18 mm	
Net weight	0.065 kg	0.065 kg	
Mounting type	2 x M18 nuts (included in scope of supply)	2 x M18 nuts (included in scope of supply)	
Cable length			
 for RS422 interface maximum 	1 000 m		
between master and IO-Link device maximum		20 m	
Product properties, functions, components general			
Display version	3-color LED	3-color LED	
Product feature silicon-free	Yes	Yes	
Standards, specifications, approvals			
Certificate of suitability	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	
MTBF	505 у	505 y	
Accessories			
Accessories		IO-Link master, IO-Link connecting cables	

RFID systems for the HF range SIMATIC RF200 readers

	91		
LL.	2 I	U	11

			111 2 1011
Selection and ordering data			Article No.
	Article No.	IO-Link connecting cables	
SIMATIC RF210R reader (RS422)	6GT2821-1AC10		
SIMATIC RF210R reader (IO-Link)	6GT2821-1AC32		
Accessories			
Note: All connection options can be found in Chapter 5, "Communication Modules".			
IO-Link master SM 1278 For SIMATIC S7-1200, for 4 readers.	6ES7278-4BD32-0XB0		
		 between IO-Link master and reader, with M12 plug on the IO-Link master, open end, 4-pole, 5 m 	6GT2891-4LH50
		 between IO-Link master and reader, with M12 plug on the IO-Link master, open end, 4-pole, 10 m 	6GT2891-4LN10
IO-Link master 4SI For SIMATIC ET 200S, for 4 readers.	6ES7138-4GA50-0AB0	 between IO-Link master and reader, with M12 plug at both ends, 4-pole, 5 m 	6GT2891-4MH50
		 between IO-Link master and reader, with M12 plug at both ends, 4-pole, 10 m 	6GT2891-4MN10
		DVD "RFID-Systems Software & Documentation"	6GT2080-2AA20
		Dimensional drawings	
IO-Link master For SIMATIC ET 200eco PN, for 4 readers.	6ES7148-6JA00-0AB0	71	
K .		SIMATIC RF210R reader	
IO-Link master	6ES7137-6BD00-0BA0	More information	
For ET 200SP, for 4 readers.		All current wireless approvals of	can be found on the Internet at:
		http://www.siemens.com/rfid-ap	oprovals
IO-Link master For ET 200AL, for 4 readers.	6ES7147-5JD00-0BA0		

SIMATIC RF200 readers

Overview





The field-proven RF210R M18 reader is integrated into the SIMATIC RF210M mobile handheld reader. It has been designed for manual workplaces and reworking stations for commissioning, as well as for tracking and tracing tasks and tool identification.

The handheld reader has an RS422 interface with 3964R transmission procedure for connection to RFID communication modules. Connection is via an 8-pole M12 plug-in connector (RS422 variant).

The handheld reader is operated with ISO 15693-compatible transponders.

Technical specifications

Article number	6GT2823-0AA00	
Product type designation	RF210M hand-held reader	
Suitability for operation	RF200/ISO 15693 transponders, to connect to communication modules via spiral cable with usable length of 2 m to 3.5 m	
Range	0 20 mm	
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	
Electrical data		
Protocol with radio transmission	ISO 15693, ISO 18000-3	
Transfer rate with radio transmission maximum	26.5 kbit/s	
Product feature multitag-capable	No	
Supply voltage, current consumption, power loss		
Type of current supply	24 V via communication module	
Type of battery	-	
Permitted ambient conditions		
Ambient temperature		
 during operation 	-20 +50 °C	
 during storage 	-25 +60 °C	
Height of fall maximum	1.5 m	
Protection class IP	IP54	

6GT2823-0AA00
RF210M hand-held reader
26 mm
140 mm
195 mm
0.46 kg
3 color LED
M12 8-pole with RS422 at spiral cable, which is permanently fixed to the reader
Function blocks for execution of ISO15693 transponders
Function blocks FB 45/55, ident profile
Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA

Selection and ordering data

	Article No.
SIMATIC RF210M handheld reader (RS422)	6GT2823-0AA00
Accessories	
Note: All connection options can be found in Chapter 5, "Communication Modules".	
DVD "RFID-Systems Software & Documentation"	6GT2080-2AA20

Dimensional drawings



SIMANG REZION Nanunelu reac

More information

All current wireless approvals can be found on the Internet at: http://www.siemens.com/rfid-approvals

RF220R

Overview



SIMATIC RF220R is an M30 reader with integrated antenna. Its compact design makes it ideal for use in small assembly lines which require a slightly higher range.

This reader has either

- an RS422 interface with 3964R transmission procedure for connection to RFID communication modules (see Chapter 5),
- or a standardized IO-Link interface for connection to IO-Link master modules from Siemens or third parties.

Thanks to its high degree of protection and rugged design, the SIMATIC RF220R reader enables problem-free use even under the toughest industrial conditions. Connection is by means of either an 8-pin M12 plug-in connector (RS422 version) or a 4-pin M12 plug-in connector (IO-Link version).

The reader is operated with ISO 15693-compatible transponders.

Design

Minimum distance from reader to reader

ISO

SIMATIC RF220R

Technical specifications

Article number	6GT2821-2AC10	6GT2821-2AC32	
Product type designation	BE220B reader	BE220B reader IO-Link	
Suitability for operation	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	ISO 15693 transponders (MDS Dxxx), for connecting to an IO-Link Master	
Wireless frequencies			
Operating frequency Rated value	13.56 MHz	13.56 MHz	
Electrical data			
Range maximum	35 mm; Range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964		
Protocol with radio transmission	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3	
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s	
Product feature multitag-capable	No	No	
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	38.4 kbit/s	
Transmission time for user data			
 for write access per byte typical 	0.6 ms	40 ms	
 for read access per byte typical 	0.6 ms	40 ms	
Interfaces			
Standard for interfaces for communication	RS422	IO-Link	
Type of electrical connection	M12, 8-pin	M12, 4-pin	
Mechanical data			
Material	Brass, nickel-plated / PBT	Brass, nickel-plated / PBT	
Color	silver/pastel turquoise	silver/pastel turquoise	
Tightening torque of the screw for securing the equipment maximum	40 Nm	40 Nm	
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm	

≥ 150 mm

RFID systems for the HF range SIMATIC RF200 readers

RF220R

Article number	6GT2821-2AC10	6GT2821-2AC32
Product type designation	BE220B reader	BE220B reader IO-Link
Supply voltage, current		
consumption, power loss		
Supply voltage		
 at DC Rated value 	24 V	24 V
at DC	20.4 28.8 V	20.4 28.8 V
Consumed current at DC at 24 V		
typical	0.05 A	0.05 A
Permitted ambient conditions		
Ambient temperature		
 during operation 	-20 +70 °C	-20 +70 °C
 during storage 	-25 +80 °C	-25 +80 °C
 during transport 	-25 +80 °C	-25 +80 °C
Protection class IP	IP67	IP67
Shock resistance	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Height	83 mm	83 mm
Diameter	30 mm	30 mm
Net weight	0.14 kg	0.14 kg
Mounting type	2 x M30 nuts (included in scope of supply)	2 x M30 nuts (included in scope of supply)
Cable length		
 for RS422 interface maximum 	1 000 m	
between master and IO-Link device maximum		20 m
Product properties, functions, components general		
Display version	3-color LED	3-color LED
Product feature silicon-free	Yes	Yes
Standards, specifications, approvals		
Certificate of suitability	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA
MTBF	501 y	501 y
Accessories		
Accessories		IO-Link master, IO-Link connecting cables

RFID systems for the HF range SIMATIC RF200 readers

			RF220
Selection and ordering data			Article No.
	Article No	IO-Link connecting cables	
SIMATIC RF220R reader	6GT2821-2AC10		
(RS422) SIMATIC RF220R reader	6GT2821-2AC32		
Accessories			
Note: All connection options can be found in Chapter 5, 'Communication Modules''.			
IO-Link master SM 1278 For SIMATIC S7-1200, for 4 readers.	6ES7278-4BD32-0XB0		
		 between IO-Link master and reader, with M12 plug on the IO-Link master, open end, 4-pole, 5 m 	6GT2891-4LH50
		 between IO-Link master and reader, with M12 plug on the IO-Link master, open end, 4-pole, 10 m 	6GT2891-4LN10
IO-Link master 4SI For SIMATIC ET 200S, for 4 readers.	6ES7138-4GA50-0AB0	 between IO-Link master and reader, with M12 plug at both ends, 4-pole, 5 m 	6GT2891-4MH50
		 between IO-Link master and reader, with M12 plug at both ends, 4-pole, 10 m 	6GT2891-4MN10
		DVD "RFID-Systems Software & Documentation"	6GT2080-2AA20
		Dimensional drawings	
IO-Link master For SIMATIC ET 200eco PN, for 4 readers.	6ES7148-6JA00-0AB0		
		SIMATIC RF220R reader	
O-Link master	6ES7137-6BD00-0BA0	More information	
		All current wireless approvals http://www.siemens.com/rfid-a	can be found on the Internet at
IO-Link master For ET 200AL, for 4 readers.	6ES7147-5JD00-0BA0		

SIMATIC RF200 readers

RF240R

Overview



SIMATIC RF240R is a reader with an integrated antenna. Its extra compact design makes it ideal for use in small assembly lines.

This reader has either

- an RS422 interface with 3964R transmission procedure for connection to RFID communication modules (see Chapter 5),
- or an RS232 interface with ASCII protocol for connection to S7-1200, PC-based systems or third-party controllers,
- or a standardized IO-Link interface for connection to IO-Link Master modules from Siemens or third parties.

Thanks to its high degree of protection and rugged design, the SIMATIC RF240R reader enables problem-free use even under the toughest industrial conditions. Connection is made either with an 8-pin M12 plug-in connector (RS422/RS232 version) or a 4-pin M12 plug-in connector (IO-Link version).

The reader is operated with ISO 15693-compatible transponders.

Design

Minimum distance from reader to reader

SIMATIC RF240R

≥ 120 mm

Technical specification	IS
-------------------------	----

Article number	6GT2821-4AC10	6GT2821-4AC40	6GT2821-4AC32
Product type designation	RF240R reader	RF240R reader ASCII	RF240R reader IO-Link
Suitability for operation	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	ISO 15693 transponders (MDS Dxxx), for connecting to PC- and control systems	ISO 15693 transponders (MDS Dxxx), for connecting to an IO-Link Master
Wireless frequencies			
Operating frequency Rated value	13.56 MHz	13.56 MHz	13.56 MHz
Electrical data			
Range maximum	65 mm; Range is dependent on transponder type: observe	65 mm; Range is dependent on transponder type: observe	65 mm; Range is dependent on transponder type: observe
	http://support.automation.siemens.com	n/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	No	No	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	115.2 kbit/s	38.4 kbit/s
Transmission time for user data			
 for write access per byte typical 	0.6 ms	1.2 ms	40 ms
 for read access per byte typical 	0.6 ms	1.2 ms	40 ms
Interfaces			
Standard for interfaces for communication	RS422	RS232	IO-Link
Type of electrical connection	M12, 8-pin	M12, 8-pin	M12, 4-pin

RFID systems for the HF range SIMATIC RF200 readers

			RF240R
Article number	6GT2821-4AC10	6GT2821-4AC40	6GT2821-4AC32
Product type designation	RF240R reader	RF240R reader ASCII	RF240R reader IO-Link
Mechanical data			
Material	PA6.6	PA6.6	PA6.6
Color	anthracite	anthracite	anthracite
Tightening torque of the screw for securing the equipment maximum	1.5 Nm	1.5 Nm	1.5 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm	0 mm
Supply voltage, current consumption, power loss			
Supply voltage			
 at DC Rated value 	24 V	24 V	24 V
• at DC	20.4 28.8 V	20.4 28.8 V	20.4 28.8 V
Consumed current at DC at 24 V			
typical	0.05 A	0.05 A	0.05 A
Permitted ambient conditions			
Ambient temperature			
 during operation 	-20 +70 °C	-20 +70 °C	-20 +70 °C
 during storage 	-25 +80 °C	-25 +80 °C	-25 +80 °C
 during transport 	-25 +80 °C	-25 +80 °C	-25 +80 °C
Protection class IP	IP67	IP67	IP67
Shock resistance	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²	200 m/s ²
Design, dimensions and weight			
Width	50 mm	50 mm	50 mm
Height	30 mm	30 mm	30 mm
Depth	50 mm	50 mm	50 mm
Net weight	0.06 kg	0.06 kg	0.06 kg
Mounting type	2 x M5 screws	2 x M5 screws	2 x M5 screws
Cable length			
 with RS232 interface maximum 		30 m	
 for RS422 interface maximum 	1 000 m		
between master and IO-Link device maximum			20 m
Product properties, functions, components general			
Display version	3-color LED	3-color LED	3-color LED
Product feature silicon-free	Yes	Yes	Yes
Standards, specifications, approvals			
Certificate of suitability	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA
MTBF	430 y	430 y	430 y
Accessories			
Accessories	Connecting cables	Connecting cables	IO-Link master, IO-Link connecting cables

RFID systems for the HF range SIMATIC RF200 readers

RF240R

Selection and ordering data

	Article No.		Article No.
SIMATIC RF240R reader (RS422)	6GT2821-4AC10	IO-Link master	6ES7147-5JD00-0BA0
SIMATIC RF240R reader (RS232 - ASCII)	6GT2821-4AC40		
SIMATIC RF240R reader (IO-Link)	6GT2821-4AC32	-0	
Accessories Note: All connection options can be found in Chapter 5, "Communication Modules".			
IO-Link master SM 1278	6ES7278-4BD32-0XB0	RS232 connecting cable	
For SIMAI IC S7-1200, for 4 readers.		 Between reader and PC (RS232), 5 m long, material: PUR, CMG approval. 24 V connection with M12 plug 	6GT2891-4KH50
IO-Link master 4SI	6ES7138-4GA50-0AB0	24 V connection with open ends	6GT2891-4KH50-0AX0
For SIMATIC ET 200S, for 4 readers.		and a state	
		IO-Link connecting cables	
IO-Link master For SIMATIC ET 200eco PN, for 4 readers.	6ES7148-6JA00-0AB0		
		\bigcirc	
		 between IO-Link Master and reader, with M12 connector on the IO-Link Master, open end, 4-pin, 5 m 	6GT2891-4LH50
IO-Link master For ET 200SP, for 4 readers.	6E\$7137-6BD00-0BA0	 between IO-Link Master and reader, with M12 connector on the IO-Link Master, open end, 4-pin, 10 m 	6GT2891-4LN10
		 between IO-Link Master and reader, with M12 connector at both ends, 4-pin, 5 m 	6GT2891-4MH50
		 between IO-Link Master and reader, with M12 connector at both ends, 4-pin, 10 m 	6GT2891-4MN10
		DVD "RFID-Systems Software & Documentation"	6GT2080-2AA20
Dimensional drawings



All current wireless approvals can be found on the Internet at: http://www.siemens.com/rfid-approvals



SIMATIC RF240R reader

SIMATIC RF200 readers

RF250R

Overview



SIMATIC RF250R is a reader for operation with external antennas. Thanks to the different antenna designs (ANT 3, ANT 3S, ANT 8, ANT 12, ANT18 and ANT 30), the potential applications in the areas of tool identification and small assembly lines are extremely varied. This reader has either

- an RS422 interface with 3964R transmission procedure for connection to RFID communication modules (see Chapter 5),
- or an RS232 interface with ASCII protocol for connection to S7-1200, PC-based systems or third-party controllers,
- or a standardized IO-Link interface for connection to IO-Link Master modules from Siemens or third parties.

Thanks to its high degree of protection and rugged design, the SIMATIC RF250R reader enables problem-free use even under the toughest industrial conditions.

Connection is made either with an 8-pin M12 plug-in connector (RS422/RS232 version) or a 4-pin M12 plug-in connector (IO-Link version).

The reader is operated with ISO 15693-compatible transponders.

Connectable antennas

One of each of the following antennas can be operated on a SIMATIC RF250R reader:

- ANT 3, due to its slimline, compact design, this antenna can still be precisely positioned even in cramped conditions. The dimensions are L x W x H (mm): 50 x 28 x 10.
- ANT 3S, same as ANT 3, except suitable exclusively for processing of MDS D117, MDS D127, MDS D421 and MDS D521 transponders. The dimensions are L x W x H (mm): 50 x 28 x 10.
- ANT 8, this cylindrical antenna is mainly intended for the field of tool identification. The extremely small design of the antenna enables extremely accurate positioning, dimensions Ø x L (mm) M8 x 38.
- ANT 12, universal round antenna in M12 design for assembly lines with extremely small workpiece holders, dimensions Ø x L (mm) M12 x 40.
- ANT 18, universal round antenna in M18 design for assembly lines with small workpiece holders, dimensions Ø x L (mm) M18 x 55.
- ANT 30, universal round antenna for assembly lines with small workpiece holders, dimensions Ø x L (mm) M30 x 58.

Design

Connectable antennas	ANT 3	ANT 3S	ANT 8	ANT 12	ANT 18	ANT 30
See page	2/132	2/133	2/134	2/136	2/137	2/138
Inductive interface to the transponder	13.56 MHz					
Range, max.	50 mm	17 mm	4 mm	17 mm	37 mm	60 mm

Minimum distance between antennas

RF250R with antenna	ANT 3	ANT 3S	ANT 8	ANT 12	ANT 18	ANT 30
Minimum distance (mm) from antenna to antenna (D)						
• ANT 3	60	-	-	-	-	-
• ANT 3S	-	80	-	-	-	-
• ANT 8	-	-	60	-	-	-
• ANT 12	-	-	-	80	-	-
• ANT 18	-	-	-	-	125	-
• ANT 30	-	-	-	-	-	200

RF250R

Technical specifications			
Article number	6GT2821-5AC10	6GT2821-5AC40	6GT2821-5AC32
Product type designation	RF250R reader	RF250R reader ASCII	RF250R reader IO-Link
Suitability for operation	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	ISO 15693 transponders (MDS Dxxx), for connecting to PC- and control systems	ISO 15693 transponders (MDS Dxxx), for connecting to an IO-Link Master
Wireless frequencies			
Operating frequency Rated value	13.56 MHz	13.56 MHz	13.56 MHz
Electrical data			
Range maximum	60 mm; Range is dependent on transponder type: observe	60 mm; Range is dependent on transponder type: observe	60 mm; Range is dependent on transponder type: observe
	http://support.automation.siemens.com	n/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	No	No	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	115.2 kbit/s	38.4 kbit/s
Transmission time for user data			
 for write access per byte typical 	0.6 ms	1.2 ms	40 ms
 for read access per byte typical 	0.6 ms	1.2 ms	40 ms
Interfaces			
Number of external antennas	1	1	1
Standard for interfaces for communication	RS422	RS232	IO-Link
Type of electrical connection			
 for external antenna(s) 	M8, 4-pin	M8, 4-pin	M8, 4-pin
 for communications interface 	M12, 8-pin	M12, 8-pin	M12, 4-pin
Mechanical data			
Material	PA6.6	PA6.6	PA6.6
Color	anthracite	anthracite	anthracite
Tightening torque of the screw for securing the equipment maximum	1.5 Nm	1.5 Nm	1.5 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm	0 mm
Supply voltage, current consumption, power loss			
Supply voltage			
 at DC Rated value 	24 V	24 V	24 V
• at DC	20.4 28.8 V	20.4 28.8 V	20.4 28.8 V
Consumed current at DC at 24 V			
• typical	0.05 A	0.05 A	0.05 A
Permitted ambient conditions			
Ambient temperature			
 during operation 	-20 +70 °C	-20 +70 °C	-20 +70 °C
 during storage 	-25 +80 °C	-25 +80 °C	-25 +80 °C
 during transport 	-25 +80 °C	-25 +80 °C	-25 +80 °C
Protection class IP	IP65	IP65	IP65
Shock resistance	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²	200 m/s ²

2

RF250R

Article number	6GT2821-5AC10	6GT2821-5AC40	6GT2821-5AC32
Product type designation	RF250R reader	RF250R reader ASCII	RF250R reader IO-Link
Design, dimensions and weight			
Width	50 mm	50 mm	50 mm
Height	30 mm	30 mm	30 mm
Depth	50 mm	50 mm	50 mm
Net weight	0.06 kg	0.06 kg	0.06 kg
Mounting type	2 x M5 screws	2 x M5 screws	2 x M5 screws
Cable length			
 with RS232 interface maximum 		30 m	
 for RS422 interface maximum 	1 000 m		
between master and IO-Link device maximum			20 m
Product properties, functions, components general			
Display version	3-color LED	3-color LED	3-color LED
Product feature silicon-free	Yes	Yes	Yes
Standards, specifications, approvals			
Certificate of suitability	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA
MTBF	430 y	430 y	430 y
Accessories			
Accessories	Various antennas are available, connecting cables	Various antennas are available, connecting cables	Various antennas are available, IO-Link master, IO-Link connecting cables

RF250R

Selection and ordering data

	Article No.
SIMATIC RF250R reader (RS422 - 3964R)	6GT2821-5AC10
Without antenna, for connecting external antennas.	
SIMATIC RF250R reader (RS232 - ASCII)	6GT2821-5AC40
Without antenna, for connecting external antennas.	
SIMATIC RF250R reader (IO-Link)	6GT2821-5AC32
Without antenna, for connecting external antennas.	
Accessories	
Note: All connection options can be found in Chapter 5, "Communication Modules".	
Antennas	
External antenna ANT 3	6GT2398-1CD40-0AX0
For RF250R reader, with antenna connecting cable (3 m, double ended (plug M8 straight / M8 angled)).	
See page 2/132.	
External antenna ANT 3S	6GT2398-1CD60-0AX0
For RF350R reader, with antenna connecting cable (3 m, double ended (plug M8 straight / M8 angled)).	
See page 2/133.	
External antenna ANT 8	6GT2398-1CF10
For RF250R reader, with antenna connecting cable (3 m), double ended (plug M8 straight / M8 angled).	
See page 2/134.	
External antenna ANT 12	6GT2398-1CC00
For RF250R readers, with antenna connecting cable.	
External antenna ANT 19	6CT2208 1CA00
For RE250B readers, with aptoppo	0012030-10A00
connecting cable.	
External antenna ANT 30	6GT2398-1CD00
For RF250R readers, with antenna	
See page 2/138.	

	Article No.
IO-Link master	
IO-Link master SM 1278	6ES7278-4BD32-0XB0
For SIMATIC S7-1200, for 4 readers.	
IO-Link master 4SI	6ES7138-4GA50-0AB0
For SIMARIC ET 2005, for 4 readers.	
IO-Link master	6ES7148-6JA00-0AB0
For SIMATIC ET 200eco PN, for 4 readers.	
IO-Link master	6ES7137-6BD00-0BA0
For ET 2005P, for 4 readers.	
IO-Link master	6ES7147-5JD00-0BA0
For ET 200AL, for 4 readers.	

SIMATIC RF200 readers

RF250R



RF260R

Overview



SIMATIC RF260R is a reader with an integrated antenna. Its compact design makes it ideal for use in assembly lines.

This reader has either:

- an RS422 interface with 3964R transmission procedure for connection to the RFID communication modules (see Chapter 5),
- an RS232 interface with ASCII protocol for connection to S7-1200, PC-based systems or third-party controllers,
- or a standardized IO-Link interface for connection to IO-Link master modules from Siemens or third parties.

Thanks to its high degree of protection and rugged design, the SIMATIC RF260R reader enables problem-free use even under the toughest industrial conditions.

Connection is by means of either an 8-pin M12 plug-in connector (RS422/RS232 version) or a 4-pin M12 plug-in connector (IO-Link version).

The reader is operated with ISO 15693-compatible transponders.

Design

Minimum distance from reader to reader	
SIMATIC RF260R	≥ 150 mm

Technical specifications

Article number	6GT2821-6AC10	6GT2821-6AC40	6GT2821-6AC32
Product type designation	RF260R reader	RF260R ASCII reader	RF260R IO-Link reader
Suitability for operation	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	ISO 15693 transponders (MDS Dxxx), for connecting to PC- and control systems	ISO 15693 transponders (MDS Dxxx), for connecting to an IO-Link Master
Wireless frequencies			
Operating frequency Rated value	13.56 MHz	13.56 MHz	13.56 MHz
Electrical data			
Range maximum	135 mm; Range is dependent on trans http://support.automation.siemens.com	ponder type: observe n/WW/view/en/67384964	
Protocol with radio transmission	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	No	No	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	115.2 kbit/s	38.4 kbit/s
Transmission time for user data			
 for write access per byte typical 	0.6 ms	1.2 ms	40 ms
 for read access per byte typical 	0.6 ms	1.2 ms	40 ms
Interfaces			
Standard for interfaces for communication	RS422	R\$232	IO-Link
Type of electrical connection	M12, 8-pin	M12, 8-pin	M12, 4-pin

SIMATIC RF200 readers

RF260R			
Article number	6GT2821-6AC10	6GT2821-6AC40	6GT2821-6AC32
Product type designation	RE260B reader	RE260B ASCII reader	RE260B IO-Link reader
Mechanical data			
Material	PA6.6	PA6.6	PA6.6
Color	anthracite	anthracite	anthracite
Tightening torque of the screw for	1.5 Nm	1.5 Nm	1.5 Nm
securing the equipment maximum			
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm	0 mm
Supply voltage, current consumption, power loss			
Supply voltage			
 at DC Rated value 	24 V	24 V	24 V
• at DC	20.4 28.8 V	20.4 28.8 V	20.4 28.8 V
Consumed current at DC at 24 V			
typical	0.05 A	0.05 A	0.05 A
Permitted ambient conditions			
Ambient temperature			
 during operation 	-20 +70 °C	-20 +70 °C	-20 +70 °C
 during storage 	-25 +80 °C	-25 +80 °C	-25 +80 °C
 during transport 	-25 +80 °C	-25 +80 °C	-25 +80 °C
Protection class IP	IP67	IP67	IP67
Shock resistance	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²	200 m/s ²
Design, dimensions and weight			
Width	75 mm	75 mm	75 mm
Height	41 mm	41 mm	41 mm
Depth	75 mm	75 mm	75 mm
Net weight	0.2 kg	0.2 kg	0.2 kg
Mounting type	2 x M5 screws	2 x M5 screws	2 x M5 screws
Cable length			
 with RS232 interface maximum 		30 m	
 for RS422 interface maximum 	1 000 m		
 between master and IO-Link device maximum 			20 m
Product properties, functions, components general			
Display version	3-color LED	3-color LED	3-color LED
Product feature silicon-free	Yes	Yes	Yes
Standards, specifications, approvals			
Certificate of suitability	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA
MTBF	480 y	430 y	480 y
Accessories			
Accessories	Connecting cables	Connecting cables	IO-Link master, IO-Link connecting cables

RF260R

Selection and ordering data

	Article No.		Article No.
SIMATIC RF260R reader (RS422)	6GT2821-6AC10	Connecting cables	
SIMATIC RF260R reader (RS232 - ASCII)	6GT2821-6AC40	RS232 connecting cable	
SIMATIC RF260R reader (IO-Link)	6GT2821-6AC32	Between reader and PC (RS232),	
Accessories		5 m, material: PUR, CMG approval. CMG-Zulassung	
Note: All connection options can be found in section 5, "Communication Modules".		• 24 V connection with M12 plug	6GT2891-4KH50
IO-Link master			
IO-Link master SM 1278	6ES7278-4BD32-0XB0	ever a second se	
For SIMATIC S7-1200, for 4 readers.		5	
		• 24 V connection with open ends	6GT2891-4KH50-0AX0
IQ-Link master 4SI	6ES7138-4GA50-0AB0	•	
For SIMATIC ET 200S, for 4 readers		IO-Link connecting cables	
			6GT2891-4LH50
IO-Link master	6ES7148-6JA00-0AB0		
For SIMATIC ET 200eco PN, for 4 readers		 between IO-Link Master and reader, 	6GT2891-4LN10
		with M12 connector on the IO-Link Master, open end. 4-pin. 5 m	
IO-Link master	6ES7137-6BD00-0BA0	 between IO-Link Master and reader, with M12 connector on the IO-Link Master, open end, 4-pin, 10 m 	6GT2891-4MH50
For ET 200SP, for 4 readers.		 between IO-Link Master and reader, with M12 connector at both ends, 4-pin, 5 m 	6GT2891-4MN10
		DVD "RFID-Systems Software & Documentation"	6GT2080-2AA20
IQ-I ink master	6ES7147-5.ID00-0BA0		
For ET 200AL, for 4 readers.	6ES/147-3JD00-0BA0		

SIMATIC RF200 readers

RF260R

Dimensional drawings



SIMATIC RF260R reader

More information

All current wireless approvals can be found on the Internet at: http://www.siemens.com/rfid-approvals

Overview



The SIMATIC RF290R reader is a compact long-range reader for the upper performance range and ranges of up to 60 cm. Intended for operation with external antennas ANT D1, ANT D5, ANT D6 and ANT D10. The application range for RF290R lies in the area of production control and intralogistics through to gate applications in which longer ranges for HF-RFID are required.

The reader is equipped with a combined RS422/RS232 interface, which is switched over when the corresponding connecting cable is used.

In RS422 mode, the reader can be connected to SIMATIC S7, PROFIBUS, PROFINET or Ethernet TCP/IP via the communication modules (see Chapter 5). Please note that due to the current consumption of the reader on the ASM 456 and RF160C, only one RF290R can be connected.

In the RS232 mode, the reader is suitable for integration into PC-based control systems. Trigger and alarm signals can be connected via digital inputs/outputs.

Furthermore, bulk detection of several hundred transponders is possible.

The antenna switch or the multiplexer enables several individual antennas or portal solutions to be implemented with only one RF290R. The RF260X antenna multiplexer supports the connection of up to 6 antennas to one reader and operates in quasi-parallel mode.

Connectable antennas

One of each of the following antennas can be operated on a SIMATIC RF290R:

- ANT D1
 - Dimensions L x W x H (mm): 75 x 75 x 20.
- ANT D5
- Dimensions L x W x H (mm): 380 x 380 x 110.
- ANT D6 Dimensions L x W x H (mm): 580 x 480 x 110.
 ANT D10
- Dimensions L x W x H (mm): 1150 x 365 x 115.

ANT D1

The ANT D1 is a universal antenna for the production and logistics areas that can also be used in dynamic applications. The high degree of protection (IP67) means the antenna can also be used under harsh industrial conditions.

ANT D5

Universal antenna for warehouse, logistics and distribution applications. The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions.

ANT D6

Antenna in the upper performance range, designed especially for warehouse, logistics and distribution applications. It can be used wherever high speeds are required together with a large write/read distance.

ANT D10

The ANT D10 is suitable for use in warehouses, logistics and distribution. An antenna with this geometry is required in the clothing industry and laundries in particular.

Design

ANT D1	ANT D5	ANT D6	ANT D10
2/139	2/141	2/143	2/145
13.56 MHz			
250 mm	480 mm	650 mm	480 mm
ANT D1	ANT D5	ANT D6	ANT D10
0,5	-	-	-
-	2	-	-
-	-	2	-
-	-	-	2
	ANT D1 2/139 13.56 MHz 250 mm ANT D1 0,5 - - -	ANT D1 ANT D5 2/139 2/141 13.56 MHz 250 mm 250 mm 480 mm ANT D1 ANT D5 0,5 - - 2 - 2 - - - 2 - - - - - - - - - - - -	ANT D1 ANT D5 ANT D6 2/139 2/141 2/143 13.56 MHz 2 250 mm 480 mm 650 mm 480 mm 650 mm ANT D1 ANT D5 ANT D6 0,5 - - - 2 - - 2 - - 2 - - - 2 - - 2

RF290R

Technical specifications

Article number	6GT2821-0AC12
Product type designation	BE290B reader
Suitability for operation	ISO 15693 transponders (MDS Dxxx)
	for connecting to communication modules and PC systems
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	650 mm;
	Hange adjustable in reader via trans- mission power, range is dependent on transponder type: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s
Product feature multitag-capable	Yes
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s
Transmission time for user data	
 for write access per byte typical 	0.6 ms
 for read access per byte typical 	0.6 ms
Interfaces	
Number of external antennas	1
Standard for interfaces for communication	RS422/RS232
Type of electrical connection	M12, 8-pin
 for external antenna(s) 	TNC
 for supply voltage 	M12, 8-pin
 for communications interface 	M12, 8-pin
 at the digital inputs/outputs 	M12, 4-pin, female connector
Number of digital inputs	1
Number of digital outputs	1
Mechanical data	
Material	aluminum
Color	silver/anthracite
Tightening torque of the screw for securing the equipment maximum	1.5 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm
Supply voltage, current consumption, power loss	
Supply voltage	
 at DC Rated value 	24 V
• at DC	21.6 26.4 V
Consumed current at DC at 24 V	
 typical 	0.4 A
• maximum	0.5 A
Permitted ambient conditions	
Ambient temperature	
 during operation 	-20 +55 °C
 during storage 	-25 +85 °C
 during transport 	-25 +85 °C
Protection class IP	IP65
Shock resistance	EN 60721-3-7 Class 7 M2
Shock acceleration	300 m/s ²
Vibrational acceleration	20 m/s ²

Article number	6GT2821-0AC12
Product type designation	RF290R reader
Design, dimensions and weight	
Width	200 mm
Height	80 mm
Depth	140 mm
Net weight	1.8 kg
Mounting type	4 x M6 screws
Cable length	
 of antenna cable minimum 	3.3 m
 of antenna cable maximum 	25 m
 with RS232 interface maximum 	30 m
 for RS422 interface maximum 	1 000 m
Product properties, functions, components general	
Display version	4 LEDs
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, IC (Canada)
MTBF	18 y
Accessories	Various antennas are available,
Accessories	antenna combiners, antenna multiplexer, mounting set for top-hat rail mounting

SIMATIC RF200 readers

RF290R

Selection and ordering data		-
	Article No.	-
SIMATIC RF290R reader	6GT2821-0AC12	-
Without antenna		
Antennas for SIMATIC RF290R		
reader		
Including antenna cable		
Antenna ANI D1	6GT2698-5AC00	
Antenna ANT D5	6GT2698-5AA10	
Antenna ANT D to	6GT2698-5AB00	
 Antenna ANT D10 Cover included in scope of delivery. 	6G12698-5AF00	
Accessories		
Note: All connection options can be found in Chapter 5, "Communication Modules".		
Antenna switch	6GT2690-0AC00	
For connecting several antennas (ANT D5, ANT D6 or ANT D10) to one reader.		
SIMATIC RF260X antenna multiplexer	6GT2894-0EA00	
Antenna multiplexer for RF290R reader when connected via RS232; 6 x antenna outputs (for ANT D5, ANT D6 and ANT D10); IP65; 240 mm x 150 mm x 70 mm; including antenna connecting cable, cable length 0.4 m.		
Image: Second		
Covering hood for ANT D6	6GT2690-0AD00	_
Serves as protection against		
contact.		
RS232 connecting cable		
Between reader and PC (RS232), 5 m long, material: PUR, CMG approval.		
 24 V connection with M12 plug 	6GT2891-4KH50	
EV		
ST ST		
24 V connection with open ends	6GT2891-4KH50-0AX0	
and the second s		

	Article No.
Accessories for antenna switch and antenna multiplexer	
Antenna connecting cable	
Between antenna and reader or antenna switch/multiplexer, PVC material.	
Length 3.3 m	6GT2691-0CH33
Length 10 m	6GT2691-0CN10
Extension cable	6GT2691-0DH72
For 6GT2691-0CH33, PVC material. Length 7.2 m.	
Standard rail mounting	6GK5798-8ML00-0AB3
DVD "RFID Systems Software & Documentation"	6GT2080-2AA20

Dimensional drawings





SIMATIC RF290R reader

More information

All current wireless approvals can be found on the Internet at: http://www.siemens.com/rfid-approvals

RFID systems for the HF range SIMATIC RF300

Overview



The RFID system SIMATIC RF300 is particularly suitable for use in industrial production in the areas of production control, assembly lines and conveyors.

SIMATIC RF300 is used to implement identification tasks with medium to high performance in the HF range (13.56 MHz).

Depending on the performance of the identification system, two versions of the system are available:

- Medium performance: System configuration with SIMATIC RF300 readers in ISO 15963 mode and low-cost MOBY D transponders.
- High performance: System configuration with SIMATIC RF300 readers in RF300 mode and SIMATIC RF300 transponders.

The SIMATIC RF300 identification system offers the following features:

- 13.56 MHz operating frequency
- For operating with ISO 15693 mode or RF300 mode
- Passive (without battery), maintenance-free transponder (MDS Dxxx and RF3xxT) with memory up to 64 KB
- Rugged, compact components with IP67 / IP68 degree of protection
- Very high immunity to noise
- Extensive diagnostic functions
- Extremely fast data transmission
- Easy integration into SIMATIC, PROFIBUS, PROFINET and TCP/IP.

Benefits

get Designed for Industry

- Rugged, compact components with high degree of protection (up to IP68).
- Data communication that is highly resistant to interference with a high degree of data security.
- Maintenance-free data carriers with up to 64 KB.
- Extremely high-speed data transmission between reader and transponder (up to 7.8 KB/s).
- Flexible and economic solutions thanks to the complete and scalable portfolio for the field of industrial identification.
- Simplified engineering, commissioning, diagnostics and maintenance through seamless integration into Totally Integrated Automation (TIA):
- Integrated bus connection to an automation system, such as SIMATIC, SIMOTION or SINUMERIK via communication modules with PROFIBUS and PROFINET.
- Simple S7 software integration via ready-to-use function blocks.
- Extensive status and diagnostic functions.
- · High investment security thanks to:
 - Open standard in accordance with ISO standard 15693.
 Software compatibility between the RFID systems of
 - Siemens.
 - Standardized communication interfaces.
- Openness through connection possibilities to various bus systems from different manufacturers and PC environments via communication modules.
- Worldwide service and support.

Application

The RFID system SIMATIC RF300 is used primarily for contactfree identification of containers, pallets and workpiece holders in a closed production cycle. This means that the data carriers (transponders, tags) remain in the production chain and are not shipped out with the products. Thanks to the compact enclosure dimensions of the transponders as well as of the read/write devices, SIMATIC RF300 is particularly suitable for (small) assembly lines where space is at a premium.

The main application areas of SIMATIC RF300 are:

- Assembly and handling systems, assembly lines (identification of workpiece carriers)
- Production logistics (material flow control, identification of containers and other vessels)
- Parts identification (e.g. transponder is attached to product or pallet)
- Conveyor systems (e.g. overhead monorail conveyors)

Introduction

Design

The high IP68 degree of protection of the SIMATIC RF300 reader enables it to be used in harsh industrial environments.

The SIMATIC RF310R, RF340R and RF380R devices have an integrated antenna. The SIMATIC RF350R reader is operated with an external antenna.

Each SIMATIC RF300 reader has a multicolor LED which locally indicates the function and status of the reader as well as of the transponder.

The interface to the automation level can be implemented by means of communication modules. For quick and easy cabling, pre-assembled cables with M12 plug-in connectors are available in various lengths.

All readers can be operated either according to the RFID standard ISO 15693, or in high-performance RF300 mode.

Depending on the mode of the reader, a comprehensive range of transponders is available for a wide variety of requirements.

For use in accordance with the ISO 15693 standard there are various versions available, e.g. low-cost SmartLabels for simple identification tasks, rugged credit card formats or screw-fit transponders that can be automatically attached by robots.

Additional transponders are available for selection for the highperformance RF300 mode, e.g. particularly heat-resistant transponders for temperatures up to +220 °C, or particularly compact rectangular designs for use on small workpiece holders.

The transponders are attached to the object to be identified, e.g. by means of screws, adhesive or pre-assembled spacer.

Function

All of the SIMATIC RF300 readers are suitable for reliable reading and writing tasks in the HF range of 13.56 MHz. In the ISO 15693 operating mode, identification tasks in the medium-performance range are possible.

The RF300 mode permits high-performance operation with a high-speed data transmission of up to 7.8 kbytes/s and is therefore one of the fastest RFID systems in the HF range.

Connection of readers to the automation level (e.g. SIMATIC S7) via standard fieldbuses (e.g. PROFIBUS or PROFINET) is by means of communication modules to which the readers can be connected via an RS422 interface.

User-friendly function blocks are available for the S7 programming.

In the event of an error, the S7 application receives a detailed error message from the communication module via the function block.

In addition, there is the option of the SIMATIC RF380R readers with an RS232 interface for the connection to the PC or to SIMATIC S7-1200.

The SIMATIC RF380R, RF382R and RF310R readers are available as <u>scan mode variants</u> (read only) for identification tasks without special command control. In these variants, the reader reads each detected transponder (UID or user data) automatically and outputs this data via the serial interface to be received by a PC, for example.

Extended diagnostics functions in RF300 mode, such as the field strength measured variable or the signature error counter, enable the HF field or the quality of the air interface to be measured.

Integration

A wide range of communication modules, function blocks, as well as high-performance drivers and function libraries permits easy and quick integration into the application.

And best of all: SIMATIC RF300 is part of Totally Integrated Automation (TIA) and can be integrated easily and cost-effectively into the SIMATIC world.

For more details on the connection possibilities, see Chapter 5 "Communication Modules".

SIMATIC Ident Configuration Guide

Here is a compact configuration tool for setting up RFID systems:

http://support.automation.siemens.com/WW/view/en/67384964

Technical specifications

RFID system	SIMATIC RF300
Transmission frequency	13.56 MHz
Maximum range	210 mm
Protocol (air interface)	• ISO 15693
	• ISO 18000-3
	RF300 (proprietary)
Approvals ¹⁾	• EN 300330, 301489, CE
	FCC Part 15
	• UL/CSA
	• ATEX
Memory capacity	Max. 64 KB
Data transmission rate reader – transponder	
• Read	Max. 7.8 kbyte/s
• Write	Max. 7.8 kbyte/s
Multitag/Bulk capability	No
Special features	High data transfer rate
	Extended diagnostic possibilities

· High memory capacity

2

 All current wireless approvals can be found on the Internet at: http://www.siemens.com/rfid-approvals

Page 2/112

2/115

2/117

RFID systems for the HF range SIMATIC RF300 readers

Introduction

Overview				
Readers	Features	Page	Readers	Features
RF310R	Ideal for use on small assembly lines.	2/105	RF380R	Ideal for use in assembly lines in which long ranges are required.
SIEMENS SIMATIC RF310R 607000-0400 91 101105874 40 4 C	The reader has an integrated antenna.		EXERCISE Control of the second secon	The reader has an integrated antenna.
RF340R	Ideal for use on assembly lines.	2/107	RF382R	Ideal for use in assembly lines in
	Reader for connecting external			which transponders must be read from the side.
SIEMENS SIMATIC REFJOR GOTOPICANO MITZHEATHER D AL A	ancinas		EXERCISE NUMBER Transmission CC	Reader with integrated special antenna. Scan mode (read only).
RF350R	Ideal for use on assembly lines.	2/109	RF350M	Mobile handheld terminal with
SIEMENE	Reader for connecting external antennas (ANT 1, 3, 3S, 12, 18, 30).		antenna.

2

SIMATIC RF300 readers

RF310R

Overview



6GT2801-1AB10

Due to its small, compact design, the SIMATIC RF310R reader can be used to considerable advantage in small assembly lines.

This reader is available with an RS422 interface for the RFID communication modules (see Chapter 5).

The SIMATIC RF310R is also available as a scan mode variant (automatic read mode, without command control). This automatic read-only mode does not require a special command control, but supplies the autonomously read transponder data directly to the connected host system.

M12, 8-pin



6GT2801-1AB20-0AX1

Due to the high degree of protection and the use of high-quality materials, the SIMATIC RF310R ensures problem-free operation even under the harshest industrial conditions. It is connected via an 8-pole M12 plug-in connector.

The reader can process the high-speed RF300 transponders and the ISO-15693-compatible transponders (see RFID systems field data table on page 1/10).

Design

Type of electrical connection

....

Minimum distance from reader to re	eader	
SIMATIC RF310R		
Technical specifications		
Article number	6GT2801-1AB10	6GT2801-1AB20-0AX1
Product type designation	RF310R reader	RF310R reader
Suitability for operation	RF300 and ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	RF300 and ISO 15693 transponders (MDS Dxxx), for serial connection to control systems (Scan Mode)
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	60 mm; Range is dependent on transponder type: obs	serve http://support.automation.siemens.com/WW/view/en/67384964
Protocol with radio transmission	RF300-specific, ISO 15693, ISO 18000-3	RF300-specific, ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	106 kbit/s	106 kbit/s
Product feature multitag-capable	No	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	115.2 kbit/s
Transmission time for user data		
 for write access per byte typical 	0.13 ms	
 for read access per byte typical 	0.13 ms	0.13 ms
Interfaces		
Standard for interfaces for communication	RS422	RS422

M12, 8-pin

SIMATIC RF300 readers

	-6	14		
- 61		21	U	E1

Article number	6GT2801-1AB10	6GT2801-1AB20-0AX1
Product type designation	RF310R reader	RF310R reader
Mechanical data		
Material	PA 12	PA 12
Color	anthracite	anthracite
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm
Supply voltage, current consumption, power loss		
Supply voltage		
 at DC Rated value 	24 V	24 V
at DC	20.4 28.8 V	20.4 28.8 V
Consumed current at DC at 24 V		
• typical	0.05 A	0.05 A
Permitted ambient conditions		
Ambient temperature		
 during operation 	-25 +70 °C	-25 +70 °C
 during storage 	-40 +85 °C	-40 +85 °C
 during transport 	-40 +85 °C	-40 +85 °C
Protection class IP	IP67	IP67
Shock resistance	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Width	55 mm	55 mm
Height	30 mm	30 mm
Depth	75 mm	75 mm
Net weight	0.2 kg	0.2 kg
Mounting type	4 x M5 screws	4 x M5 screws
Cable length		
 for RS422 interface maximum 	1 000 m	1 000 m
Product properties, functions, components general		
Display version	3-color LED	3-color LED
Product feature silicon-free	Yes	Yes
Standards, specifications, approvals		
Certificate of suitability	Wireless according to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, UL/CSA	Wireless according to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, UL/CSA
MTBF	154 у	170 у

Selection and ordering data

	Article No.
SIMATIC RF310R reader	
With RS422 interface (3964R protocol)	6GT2801-1AB10
• as a scan mode variant (RS422)	6GT2801-1AB20-0AX1
Accessories	
Note: All connection options can be found in the chapter 5 "Communication Modules".	
DVD "RFID-Systems Software & Documentation"	6GT2080-2AA20

More information

All current wireless approvals can be found on the Internet at:

http://www.siemens.com/rfid-approvals

Dimensional drawings



SIMATIC RF310R reader without Scan Mode

RF340<u>R</u>

2



The SIMATIC RF340R is a reader with integrated antenna for the medium performance range and can be used to great advantage in assembly lines thanks to its compact design. This reader is also particularly suitable for dynamic applications, in which the transponder does not stop during the read/write process.

This reader has an RS422 interface with 3964R transmission procedure for connection to RFID communication modules (see Chapter 5).

Thanks to the high degree of protection and the use of high-quality materials, the SIMATIC RF340R ensures problem-free use even under the toughest industrial conditions. It is connected via an 8-pole M12 plug-in connector.

The reader can process the high-speed RF300 transponders and the ISO-15693-compatible transponders (see RFID systems field data table on page 1/10).

Design

Minimum distance from reader to reader		
SIMATIC RF340R ≥ 200 mm		
Technical specifications		
Article number	6CT2001 2AB10	

Article number	6G12801-2AB10
Product type designation	RF340R reader
Suitability for operation	RF300 and ISO 15693 transponder (MDS Dxxx), for connecting to communication modules
Vireless frequencies	

Operating frequency Rated value

13.56 MHz

'S

Article number	6GT2801-2AB10
Product type designation	RF340R reader
Elektrische Daten	
Range maximum	140 mm; Range is dependent on transponder type: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	RF300-specific, ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	106 kbit/s
Product feature multitag-capable	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s
Transmission time for user data	
 for write access per byte typical 	0.13 ms
 for read access per byte typical 	0.13 ms
Interfaces	
Standard for interfaces for communication	RS422
Type of electrical connection	M12, 8-pin
Mechanical data	
Material	PA 12
Color Mounting distance relating to motal	anthracite
surfaces recommended minimum	0 mm
Supply voltage, current consumption, power loss	
Supply voltage	
 at DC Rated value 	24 V
• at DC	20.4 28.8 V
Consumed current at DC at 24 V	0.1.4
	0.1 A
Ambient temperature	
during operation	25 , 70 °C
during operation	-20 +85 °C
during transport	-40 +85 °C
Protection class IP	IP67
Shock resistance	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Width	75 mm
Height	41 mm
Depth	75 mm
Net weight	0.25 kg
Mounting type	2 x M5 screws
Cable length	1.000
for RS422 Interface maximum	1 000 m
components general	
Display version	3-color LED
Product feature silicon-free	res
standards, specifications, approvals	
Certificate of suitability	Wireless according to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, UL/CSA, Fx:
MTDE	II 3G Ex nA nC IIB T5, II 3D Ex tD A22 IP6x T80°C
NIIRF	140 y

SIMATIC RF300 readers

RF340R

Selection and ordering data

Dimensional	drawings
Dimensional	aramigo

Article No.		
SIMATIC RF340R reader	6GT2801-2AB10	
Accessories		
Note: All connection options can be found in section 5, "Communication Modules".		
DVD "RFID-Systems Software & Documentation"	6GT2080-2AA20	



SIMATIC RF340R reader

More information

All current wireless approvals can be found on the Internet at: http://www.siemens.com/rfid-approvals

RF<u>350R</u>

Overview



SIMATIC RF350R is a universal reader for operation with external antennas. Due to the different, pluggable antenna designs (flat antenna, round antennas), there are many possible applications in the area of industrial production, especially in assembly lines.

This reader has an RS422 interface with 3964R transmission procedure for connection to RFID communication modules (see Chapter 5).

Due to the high degree of protection and the use of high-quality materials, the SIMATIC RF350R ensures problem-free operation even under the harshest industrial conditions. It is connected via an 8-pole M12 plug-in connector.

The reader can process the high-speed RF300 transponders and the ISO-15693-compatible transponders (see RFID systems field data table on page 1/10).

Connectable antennas

One of each of the following antennas can be operated on an RF350R:

- ANT 1, universal flat antenna, also for dynamic applications, dimensions L x W x H (mm): 75 x 75 x 20
- Due to its slimline, compact design, the ANT 3 can still be precisely positioned even in cramped conditions. Dimensions L x W x H (mm): 50 x 28 x 10
- ANT 3S, same as ANT 3, except suitable exclusively for processing of MDS D117, MDS D127, MDS D421 and MDS D521 transponders. The dimensions are L x W x H (mm): 50 x 28 x 10.
- ANT 12, universal round antenna in M12 design for assembly lines with extremely small workpiece holders. Dimensions Ø x L (mm): M12 x 40
- ANT 18, universal round antenna in M18 design for assembly lines with small workpiece holders. Dimensions Ø x L (mm): M18 x 55
- ANT 30, universal round antenna for assembly lines with small workpiece holders.
 Dimensions Ø x L (mm): M30 x 58

Design

Connectable antennas	ANT 1	ANT 3	ANT 3S	ANT 12	ANT 18	ANT 30
See page	2/131	2/132	2/133	2/136	2/137	2/138
Inductive interface to the transponder	13.56 MHz					
Range, max	140 mm	45 mm	16 mm	16 mm	35 mm	55 mm

Minimum distance between antennas

RF350R with antenna	ANT 1	ANT 3	ANT 3S	ANT 12	ANT 18	ANT 30
Minimum distance (mm) from antenna to antenna (D)						
• ANT 1	800	-	-	-	-	-
• ANT 3	-	200	-	-	-	-
• ANT 3S	-	-	80	-	-	-
• ANT 12	-	-	-	80	-	-
• ANT 18	-	-	-	-	125	-
• ANT 30	-	-	-	-	-	200

RF350R

Technical specifications

Article number	6GT2801-4AB10
Product type designation	RF350R reader
Suitability for operation	RF300 and ISO 15693 transponders (MDS Dxxx), for connecting to communication modules
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	140 mm; Range is dependent on transponder type: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	RF300-specific, ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	106 kbit/s
Product feature multitag-capable	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s
Transmission time for user data	
 for write access per byte typical 	0.13 ms
 for read access per byte typical 	0.13 ms
Interfaces	
Number of external antennas	1
Standard for interfaces for communication	RS422
Type of electrical connection	
 for external antenna(s) 	M8, 4-pin
 for communications interface 	M12, 8-pin
Mechanical data	
Material	PA 12
Color	anthracite
Mounting distance relating to metal surfaces recommended minimum	0 mm
Supply voltage, current consumption, power loss	
Supply voltage	
 at DC Rated value 	24 V
• at DC	20.4 28.8 V
Consumed current at DC at 24 V	
• typical	0.1 A
Permitted ambient conditions	
Ambient temperature	
 during operation 	-25 +70 °C
 during storage 	-40 +85 °C
 during transport 	-40 +85 °C
Protection class IP	IP65
Shock resistance	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Width	75 mm
Height	41 mm
Depth	75 mm
Net weight	0.25 kg
Mounting type	2 x M5 screws
Cable length	
of antenna cable fixed value	3 m
 for RS422 interface maximum 	1 000 m

Article number	6GT2801-4AB10
Product type designation	RF350R reader
Product properties, functions, components general	
Display version	3-color LED
Product feature silicon-free	Yes
Standards, specifications, approvals	
Certificate of suitability	Wireless according to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, UL/CSA,
	Ex: II 3G Ex nA nC IIB T5, II 3D Ex tD A22 IP6x T80°C
MTBF	140 y
Accessories	Various antennas are available

Selection and ordering data

	Article No.
SIMATIC RF350R reader	6GT2801-4AB10
Without antenna	
Antennas	
External antenna ANT 1	6GT2398-1CB00
For RF350R reader, with antenna connecting cable (3 m, permanently connected to antenna ANT 1).	
See page 2/131.	
External antenna ANT 3	6GT2398-1CD40-0AX0
For RF350R reader, with antenna connecting cable (3 m, double ended (plug M8 straight / M8 angled)). See page 2/132.	
External antenna ANT 3S	6GT2398-1CD60-0AX0
For RF350R reader, with antenna connecting cable (3 m, double ended (plug M8 straight / M8 angled)).	
See page 2/133.	
External antenna ANT 12	6GT2398-1CC00
For RF350R readers, with antenna connecting cable.	
See page 2/136.	
External antenna ANT 18	6GT2398-1CA00
For RF350R readers, with antenna connecting cable.	
See page 2/137.	
External antenna ANT 30	6GT2398-1CD00
For RF350R readers, with antenna connecting cable.	
Accessories	
All connection options can be found in the chapter 5 "Communication Modules".	
DVD "RFID-Systems Software & Documentation"	6GT2080-2AA20

Dimensional drawings

SIMATIC RF350R reader



More information

All current wireless approvals can be found on the Internet at: http://www.siemens.com/rfid-approvals

SIMATIC RF300 readers

RF380R

Overview



SIMATIC RF380R is a reader with an integral antenna for the top-

end performance range and its compact construction makes it

ideal for use in assembly lines in which long ranges are required

(e.g. bodyshop/paintshop in the automotive industry). This

reader is also particularly suitable for dynamic applications,

process (e.g. baggage conveyors in airports).

as well as to non-Siemens controllers or the PC.

in which the transponder does not stop during the read/write

This reader has both an RS422 and an RS232 interface with

a 3964R transmission procedure for connection to RFID

communication modules (see Communication modules)





Scanmode

6GT2801-3AB20-0AX1

The RF380R is also available as a scan mode variant (automatic read mode, without command control). This automatic read-only mode does not require a special command control, but supplies the autonomously read transponder data directly to the connected host system.

Due to the high degree of protection and the use of high-quality materials, the SIMATIC RF380R facilitates problem-free operation even under the harshest industrial conditions. It is connected via an 8-pole M12 plug-in connector.

The reader can process the high-speed RF300 transponders and the ISO-15693-compatible transponders (see RFID systems field data table on page 1/10).

Design

Speed

6GT2801-3AB10

Minimum distance from reader to reader

SIMATIC RF380R



RF380R

Technical specifications		
Article number	6GT2801-3AB10	6GT2801-3AB20-0AX1
Product type designation	RF380R reader	RF380R reader (ISO scan mode)
Suitability for operation	RF300 and ISO 15693 transponders (MDS Dxxx), for connecting to communication modules and PC systems	RF300 and ISO 15693 transponders (MDS Dxxx), s for serial connection to control systems (Scan Mode)
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Range maximum	200 mm; Range adjustable in reader via transmission power, range i http://support.automation.siemens.com/WW/view/en/67384	200 mm is dependent on transponder type: observe 964
Protocol with radio transmission	RF300-specific, ISO 15693, ISO 18000-3	RF300-specific, ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	106 kbit/s	106 kbit/s
Product feature multitag-capable	No	No
Transfer rate at the point-to-point connection serial maximum Transmission time for user data	115.2 kbit/s	115.2 kbit/s
 for write access per byte typical 	0.13 ms	
 for read access per byte typical 	0.13 ms	0.13 ms
Interfaces		
Standard for interfaces for communication	R\$422/R\$232	RS422/RS232
Type of electrical connection	M12, 8-pin	M12, 8-pin
Mechanical data		
Material	PA 12	PA 12
Color	anthracite	anthracite
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm
Supply voltage, current consumption, power loss		
Supply voltage		
 at DC Rated value 	24 V	24 V
• at DC	20.4 28.8 V	20.4 28.8 V
Consumed current at DC at 24 V		
• typical	0.16 A	0.16 A
Permitted ambient conditions		
Ambient temperature		
 during operation 	-25 +70 °C	-25 +70 °C
 during storage 	-40 +85 °C	-40 +85 °C
 during transport 	-40 +85 °C	-40 +85 °C
Protection class IP	IP67	IP67
Shock resistance	EN 60721-3-7, Class 7 M2	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Width	80 mm	80 mm
Height	41 mm	41 mm
Depth	160 mm	160 mm
Net weight	0.6 kg	0.6 kg
Mounting type	4 x M5 screws	4 x M5 screws
Cable length		
 with RS232 interface maximum 	30 m	30 m
 for RS422 interface maximum 	1 000 m	1 000 m
Product properties, functions, components general		
Display version	3-color LED	3-color LED
Product feature silicon-free	Yes	Yes
Standards, specifications, approvals		
Certificate of suitability	Wireless according to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, UL/CSA,	Wireless according to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, UL/CSA,
	Ex: II 3G Ex nC IIB T5	Ex: II 3G Ex nC IIB T5
MTBF	109 y	109 y

SIMATIC RF300 readers

RF380R

Selection and ordering data

	Article No.		Article No.
SIMATIC RF380R reader		Accessories	
 RF300 and ISO15693 modes 	6GT2801-3AB10	Note:	
scan mode	6GT2801-3AB20-0AX1	All connection options can be found in section 5, "Communication Modules".	
		RS232 connecting cable	
		Between reader and PC (RS232), 5 m long, material: PUR, CMG approval.	
		 24 V connection with M12 plug 	6GT2891-4KH50
		CONTRACTOR OF	
		 24 V connection with open ends 	6GT2891-4KH50-0AX0
		and the second sec	
		DVD "RFID-Systems Software & Documentation"	6GT2080-2AA20

Dimensional drawings



SIMATIC RF380R reader

More information

All current wireless approvals can be found on the Internet at: http://www.siemens.com/rfid-approvals

≥ 200 mm

RFID systems for the HF range SIMATIC RF300 readers

RF<u>382R</u>

Overview



SIMATIC RF382R is a reader with an integral special antenna for the top-end performance range and its compact construction makes it ideal for implementation in conveyor systems in which transponders have to be read from the side (e.g. in the clothing industry or laundry applications). This reader is also particularly suitable for dynamic applications, in which the transponder does not stop during the read/write process.

The reader has both an RS422 interface and an RS232 interface with scan mode functionality. This automatic read-only mode does not require a special command control, but supplies the autonomously read transponder data directly to the connected host system.

Due to the high degree of protection and the use of high-quality materials, the SIMATIC RF382R facilitates problem-free operation even under the harshest industrial conditions. It is connected via an 8-pole M12 plug-in connector.

The reader can process the high-speed RF300 transponders and the ISO-15693-compatible transponders (see RFID systems field data table on page 1/10).

Design

Minimum distance from reader to reader

SIMATIC RF382R

Technical specifications

Article number	6GT2801-3AB20-0AX0
Product type designation	RF382R reader
Suitability for operation	RF300 and ISO 15693 transponders (MDS Dxxx), lateral antenna field, for serial connection to control systems (Scan Mode)
Wireless frequencies	
Operating frequency Rated value	13.56 MHz
Electrical data	
Range maximum	75 mm; Range adjustable in reader via trans- mission power, range is dependent on transponder type: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	RF300-specific, ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	106 kbit/s
Product feature multitag-capable	No
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s
Transmission time for user data	
 for read access per byte typical 	0.13 ms
Interfaces	
Standard for interfaces for communication	RS422/RS232
Type of electrical connection	M12, 8-pin
Mechanical data	
Material	PA 12
Color	anthracite
Mounting distance relating to metal surfaces recommended minimum	0 mm

Article number	6GT2801-3AB20-0AX0
Product type designation	RF382R reader
Supply voltage, current consumption, power loss	
Supply voltage	
 at DC Rated value 	24 V
• at DC	20.4 28.8 V
Consumed current at DC at 24 V	
typical	0.16 A
Permitted ambient conditions	
Ambient temperature	
 during operation 	-25 +70 °C
 during storage 	-40 +85 °C
 during transport 	-40 +85 °C
Protection class IP	IP67
Shock resistance	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²

RF382R

Article number	6GT2801-3AB20-0AX0	Selection and ordering data	
Product type designation	RF382R reader		
Design, dimensions and weight			Article No.
Width	80 mm	SIMATIC RF382R reader	6GT2801-3AB20-0AX0
Height	41 mm	RF300 and ISO15693 modes.	
Depth	160 mm	Accessories	
Net weight	0.6 kg	BS232 connecting cable	
Mounting type	4 x M5 screws		
Cable length		5 m long, material: PUR.	
 with RS232 interface maximum 	30 m	CMG approval.	
 for RS422 interface maximum 	1 000 m	 24 V connection with M12 plug 	6GT2891-4KH50
Product properties, functions, components general			
Display version	3-color LED		
Product feature silicon-free	Yes		
Standards, specifications, approvals		in the second se	
Certificate of suitability	Wireless according to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, UL/CSA	24 V connection with open ends	6GT2891-4KH50-0AX0
MTBF	109 y	and the second se	
Accessories			
Accessories	RS232 connecting cables	and the	

DVD "RFID-Systems Software & Documentation"

6GT2080-2AA20

Dimensional drawings



SIMATIC RF382R reader

RF350M mobile handheld terminal

Overview





The SIMATIC RF350M is a powerful mobile handheld terminal for applications in the field of production logistics, distribution and service. In addition, it is an indispensable tool for commissioning and testing. The RF350M is equipped either with an integral antenna or with a socket for connecting external antennas.

Design

The SIMATIC RF350M mobile handheld terminal consists of a basic unit (Basis Nordic ID Merlin) and an integrated read/write device for RF300 transponders and transponders of the MDS D-family according to the ISO15693 standard. The read/ write device is equipped either with an integrated antenna or with a socket for connecting external antennas.

The SIMATIC RF350M has a splash-proof enclosure (IP54), a color QVGA color touchscreen with a resolution of 320 x 240 pixels, TFT portrait format, an alphanumeric keyboard and various interfaces e.g. for SD memory cards, battery charging and WLAN.

Integral read/write unit, inductive interface to transponder	For SIMATIC RF300 / RF200, MOBY D (ISO)
Read/write distance to the tran-	• RF300: up to 50 mm
sponder (with integrated antenna)	ISO: up to 80 mm
Read/write distance to the tran- sponder (with external antenna)	• RF300: up to 30 mm
	• ISO: up to 60 mm
Energy/data transmission frequency	13.56 MHz
Serial interface (internal, to basic unit)	RS232, 3964R protocol
Functionality of the software application	Standard user interface for read- ing/writing of transponders, etc.

Function

The supplied and pre-installed software provides the following service and test functions for RF300 and MDS Dxxx transponders¹⁾:

- Reading data from the transponder
- · Writing data to the transponder
- Reading and displaying the ID number of the transponder
- Displaying and editing the data in hexadecimal, ASCII, decimal and binary formats

Based on the operating system and communication standard (WIN CE), the unit ensures simple integration into existing or planned infrastructures. Various optional development tools for the PC and a wide selection of accessories are available.

Connectable antennas

One of each of the following antennas can be operated on a SIMATIC RF350M for external antennas:

- ANT 3.
- Dimensions L x W x H (mm): 28 x 50 x 10 ANT 3S.
- Dimensions L x W x H (mm): 28 x 50 x 10
- ANT 8,
 Dimensions Ø x L (mm): M8 x 38
- ANT 12,
- Dimensions Ø x L (mm): M12 x 40 • ANT 18,
- Dimensions Ø x L (mm): M18 x 55 • ANT 30.
- Dimensions Ø x L (mm): M30 x 58

¹⁾ Exception: The MDS D421, MDS D422, MDS D127 and MDS D117 transponders can only be operated with the SIMATIC RF350M mobile handheld terminal with external antenna..

RF350M mobile handheld terminal

Technical specifications

Article number	6GT2803-1BA00	6GT2803-1BA10
Product type designation	RF350M mobile hand-held terminal	RF350M mobile hand-held terminal for external antenna
Suitability for operation	RF300- and RF200/ISO 15693 transponders	RF300- and RF200/ISO 15693 transponders, in particular for small transponders
Range	80 mm	80 mm
Range note		dependent of the type of external antenna
Wireless frequencies		
Operating frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Protocol with radio transmission	RF300-specific, ISO 15693, ISO 18000-3	RF300-specific, ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	106 kbit/s	106 kbit/s
Product feature multitag-capable	No	No
Supply voltage, current consumption, power loss		
Type of current supply	Battery operation or mains operation via docking station	Battery operation or mains operation via docking station
Type of battery	Lithium ion accumulator, fast charging capability	Lithium ion accumulator, fast charging capability
Type of battery as back-up battery Integrated	Lithium ion battery, permanently installed, cannot be replaced by customer	Lithium ion battery, permanently installed, cannot be replaced by customer
Battery capacity	2.6 Ah	2.6 Ah
Operating period with standard battery typical	8 h	8 h
Permitted ambient conditions		
Ambient temperature		
 during operation 	-20 +55 °C	-20 +55 °C
during storage	-20 +60 °C	-20 +60 °C
Relative humidity at 25 °C without	95 %	95 %
condensation during operation maximum		
Height of fall maximum	1.2 m	1.2 m
Protection class IP	IP54	IP54
Design, dimensions and weight		
Width	90 mm	90 mm
Height	250 mm	250 mm
Depth	47 mm	47 mm
Net weight	0.6 kg	0.6 kg
Product properties, functions, components general		
Design of the display	QVGA color touch screen 3.5 inch, 240 x 320 pixels	QVGA color touch screen 3.5 inch, 240 x 320 pixels
Operator element version	Alphanumeric	Alphanumeric
Design of acoustic signaling element	Speakers	Speakers
Design of the interface	WLAN, USB and Ethernet via charging station	WLAN, USB and Ethernet via charging station
Storage capacity		
 of the RAM 	256 Mibyte	256 Mibyte
 of the data and program memory 	288 Mibyte	288 Mibyte
of the data memory can be used	256 Mibyte	256 Mibyte
Product functions management, configuration		
Operating system pre-installed	Windows Embedded CE 6.0	Windows Embedded CE 6.0
Product function of the software	RF350M.exe for execution of RF300 and ISO15693 (RF200, MOBY D) transponders	RF350M.exe for execution of RF300 and ISO15693 (RF200, MOBY D) transponders
Standards, specifications, approvals		
Certificate of suitability	EMC: EN 55022, EN 301 489, EN 300 330, EN 300 328, EN 301 893, safety: EN 60950	EMC: EN 55022, EN 301 489, EN 300 330, EN 300 328, EN 301 893, safety: EN 60950
Accessories		
Accessories	Charging/docking station with USB- and Ethernet interface, changeable accumulator Li-ion 2600 mAh / 7.4 V	Charging/docking station with USB- and Ethernet interface, changeable accumulator Li-ion 2600 mAh / 7.4 V external antenna ANT 3, ANT 3S, ANT 8, ANT 12, ANT 18, ANT 30, Charge and Charge

RF350M mobile handheld terminal

Selection and ordering data

	Article No.		Article No.
SIMATIC RF350M mobile handheld terminal • Basic unit with integrated RFID read/write unit (RF300 and ISO 15693), integrated antenna, battery, standard software pre-in-	6GT2803-1BA00	Accessories Note: All connection options can be found in Chapter 5, "Communication Modules".	
 stalled, without charging/docking station. Basic unit with integrated RFID read/write unit (RF300 and ISO 15693), for external antennas, battery, standard software pre-installed, without charging/docking station, without external antenna. 	6GT2803-1BA10	Charging/docking station For a mobile handheld terminal as well as a spare battery, including wide-range plug-in power supply 100 to 240 V AC and country- specific adapters as well as USB cable.	6GT2803-0BM00
External antennas for 6GT2803-1BA10			
External antenna ANT 3 For RF350M mobile handheld terminal (6GT2803-1BA10), without antenna connecting cable. See page 2/132.	6GT2398-1CD30-0AX0		
External antenna ANT 3S For RF350M mobile handheld terminal (6GT2803-1BA10), without antenna connecting cable. See page 2/133.	6GT2398-1CD50-0AX0	Spare battery For basic device, 2600 mAh, Licion batteries	6GT2803-0CA00
External antenna ANT 8 For RF350M mobile handheld terminal (6GT2803-1BA10), without antenna connecting cable.	6GT2398-1CF00	DVD "RFID-Systems Software & Documentation"	6GT2080-2AA20
See page 2/134.		Dimensional drawings	
Antenna adapter for ANT 3, ANT 3S and ANT 8 For direct connection of ANT 3, ANT 3S and ANT 8 to RF350M (6GT2803-1BA10). • Length 0.1 m	6GT2898-0EA00		170
Length 3 m	6GT2391-0AH30		
External antenna ANT 12 For RF350M mobile handheld terminal, with antenna connecting cable.	6GT2398-1CC00		\$7,01159
See page 2/136.	CCT0200 1CA00		S10
External antenna ANI 18 For RF350M mobile handheld terminal, with antenna connecting cable.	6G12398-1CA00	Deaking station for SIMATIC PE2EC	ت M bandhald terminal
See page 2/137.			
External antenna ANT 30 For RF350M mobile handheld terminal, with antenna connecting cable. See page 2/138.	6GT2398-1CD00	More information All current wireless approvals of http://www.siemens.com/rfid-ap	can be found on the Internet at: oprovals

Overview



The MOBY D RFID system is particularly suitable for use in industrial production in the areas of production control, asset management and tracking & tracing.

MOBY D is used for implementing identification tasks with medium performance (ISO 15693) in the HF range (13.56 MHz).

MOBY D offers a comprehensive portfolio of ISO 15693 transponders for a whole variety of requirements - from low-cost SmartLabels for simple identification tasks through rugged credit card formats, right up to transponders for use in especially harsh environments such as paint shops or in the laundry and cleaning industry.

The communication modules that can be used for all MOBY and SIMATIC RF systems (ASM 456, ASM 475, SIMATIC RF1xxC) are available for connecting to SIMATIC S7-300, PROFIBUS, PROFINET and TCP/IP (XML).

Depending on the read/write distance, different readers are available with integrated or remote antennas.

The MOBY D identification system boasts the following performance features:

- 13.56 MHz operating frequency.
- · Operation according to ISO 15693.
- Passive (without battery), maintenance-free transponder (MDS Dxxx) with memory of up 2 000 bytes FRAM.
- Rugged, compact components with IP68 / IPx9K degree of protection.
- Simple integration in SIMATIC, PROFIBUS, PROFINET and TCP/IP with the help of tried and tested function blocks (FC 45, FB 45).

Benefits

9 Get Designed for Industry

- High-performance reader with bulk detection capability and a range of up to 0.35 m.
- Cost-effective and battery-free ISO 15963 transponders up to 2 KB with IP68 degree of protection and 220 °C temperature range, with ATEX approval.
- Flexible and economic solutions thanks to the complete and scalable portfolio for the field of industrial identification.

- Simplified engineering, commissioning, diagnostics and maintenance through seamless integration into Totally Integrated Automation (TIA):
 - Integrated bus connection to an automation system, such as SIMATIC, SIMOTION or SINUMERIK via communication modules with PROFIBUS and PROFINET.
- Simple S7 software integration via ready-to-use function blocks.
- High security of investment thanks to:
- Ŏpen ISO 15693 standard.
- Software compatibility between the RFID systems of Siemens.
- Standardized communication interfaces.
- Openness through connection possibilities to different bus systems from different manufacturers and PC environments via communication modules.
- Worldwide Service and Support.

Application

- High-performance reader with bulk detection capability and a range of up to 0.35 m.
- Cost-effective and battery-free ISO 15963 transponders up to 2 KB with IP68 degree of protection and 220 °C temperature range, with ATEX approval.
- Flexible and economic solutions thanks to the complete and scalable portfolio for the field of industrial identification.
- Simplified engineering, commissioning, diagnostics and maintenance through seamless integration into Totally Integrated Automation (TIA):
- Integrated bus connection to an automation system, such as SIMATIC, SIMOTION or SINUMERIK via communication modules with PROFIBUS and PROFINET.
- Simple S7 software integration via ready-to-use function blocks.
- · High security of investment thanks to:
 - Open ISO 15693 standard.
 - Software compatibility between the RFID systems of Siemens.
 - Standardized communication interfaces.
- Openness through connection possibilities to different bus systems from different manufacturers and PC environments via communication modules.
- Worldwide Service and Support.

Design

The MOBY D readers are available in different designs. In addition to the SLG D12 and SLG D12S readers with integrated antennas, the SLG D11 and SLG D11S readers permit the connection of various external antennas with which extended ranges of up to 380 mm can be achieved.

The high degree of protection of up to IP65 enables the MOBY D readers to be used in harsh, industrial environments.

The interface to the automation level can be implemented by means of communication modules. For quick and easy cabling, pre-assembled cables with M12 plug-in connectors are available in various lengths.

The MOBY D transponders compliant with ISO 15693 are used as mobile data carriers.

Transponders suitable for a wide variety of different requirements can be selected from an extensive range: From low-cost SmartLabels for simple identification tasks, through rugged credit card formats, right up to screw-fit transponders that can be automatically attached by robots.

The transponders are attached to the object to be identified, e.g. by means of screws, adhesive or pre-assembled spacer.

Function

All MOBY D readers are suitable for reliable reading and writing tasks in the HF range.

The readers are equipped either with an RS232 interface for the connection to the PC or to SIMATIC S7-1200 or with an RS422 interface for the connection via communication modules to the automation level (e.g. SIMATIC S7) via standard fieldbuses (e.g. PROFIBUS or PROFINET).

User-friendly function blocks are available for the S7 programming.

In the event of an error, the S7 application receives a detailed error message from the communication module via the function block.

Integration

A wide range of communication modules, function blocks, as well as high-performance drivers and function libraries permits easy and quick integration into the application.

And best of all: MOBY D is part of Totally Integrated Automation (TIA) and can be integrated easily and cost-effectively into the SIMATIC world.

For more details on the connection possibilities, see the section 5 "Communication Modules".

SIMATIC Ident Configuration Guide

Here is a compact configuration tool for setting up RFID systems:

http://support.automation.siemens.com/WW/view/en/67384964

Technical specifications

RFID system	MOBY D
Transmission frequency	13.56 MHz
Range	Max. 380 mm
Protocol (air interface)	• ISO 15693
	• ISO 18000-3
Approvals	• EN 300330, 301489, CE
	FCC Part 15
	• UL/CSA
Memory capacity	992 bytes (EEPROM) / 2 000 bytes (FRAM)
Data transmission rate reader – transponder	
• Read	Max. 1.5 kbyte/s
• Write	Max. 0.5 kbyte/s
Multitag/Bulk capability	Yes
Special features	SIMATIC or PC/IT integration
	 Long sensing ranges with excellent interference immunity

• External antennas for industrial applications

RFID systems for the HF range MOBY D readers

Introduction

Readers	Features	Page	Readers	Features	Page
SLG D11 basic unit	Reader for connection of an exter- nal antenna (ANT D2 / ANT D5). With RS232 interface for connection to PC/PLC.	2/123	SLG D12	Universal reader with integrated antenna. With RS232 interface for connection to PC/PLC.	2/126
SLG D11S basic unit	Like SLG D11, but with RS422 interface for connection to SIMATIC S7 / PROFIBUS / PROFINET / Ethernet TCP/IP via ASM 456, ASM 475, SIMATIC RF120C, RF160C, RF170C, RF180C or RF182C.	2/123	SLG D12S	Like SLG D12, but with RS422 interface for connection to SIMATIC S7 / PROFIBUS / PROFINET / Ethernet TCP/IP via ASM 456, ASM 475, SIMATIC RF120C, RF160C, RF170C, RF180C or RF182C.	2/126

SLG D11/SLG D11S basic unit for ANT D2 and ANT D5 antennas

Overview



The SLG D11/SLG D11S basic units are readers in the midperformance range and can be operated with the ANT D2 and ANT D5 antennas.

SLG D11

Equipped with RS232 serial interface for connection to PC/PLC.

SLG D11S

Equipped with an RS422 serial interface, which permits communication via the communication modules ASM 456, ASM 475, SIMATIC RF120C, RF160C, RF170C and SIMATIC RF180C, or RF182C to SIMATIC S7, PROFIBUS/PROFINET or Ethernet TCP/IP.

Connectable antennas

ANT D2

The ANT D2 antenna is designed for transponders that are directed sideways past the antenna. This antenna is specially designed for high speeds, e.g. in overhead conveyors, assembly lines, production and order picking. It can be mounted directly onto metal surfaces. Description see page 2/140.

ANT D5

The ANT D5 is a universal antenna designed for warehouse, logistics and distribution applications. The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions. A spacer kit is required for mounting on metal surfaces. Description see page 2/141.

Technical specifications

·			
Article number	6GT2698-1AC00	6GT2698-2AC00	
Product type designation	SLG D11 reader	SLG D11S reader	
Suitability for operation	ISO 15693 transponders (MDS Dxxx), for connecting to PC systems	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	
Wireless frequencies			
Operating frequency Rated value	13.56 MHz	13.56 MHz	
Electrical data			
Range maximum	380 mm; Range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964		
Protocol with radio transmission	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3	
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s	
Product feature multitag-capable	Yes	No	
Transfer rate at the point-to-point connection serial maximum	38.4 kbit/s	19.2 kbit/s	
Transmission time for user data			
 for write access per byte typical 	2.5 ms	2.5 ms	
 for read access per byte typical 	2.5 ms	2.5 ms	
Interfaces			
Number of external antennas	1	1	
Standard for interfaces for communication	RS232	RS422	
Type of electrical connection			
 for external antenna(s) 	TNC	TNC	
 for supply voltage 	M12, 4-pin, female connector	M12, 4-pin, female connector	
 for communications interface 	Sub-D, 9-pin, male	Sub-D, 9-pin, male	
Mechanical data			
Material	PA 12	PA 12	
Color	anthracite	anthracite	
Tightening torque of the screw for securing the equipment maximum	2 Nm	2 Nm	
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm	

2

RFID systems for the HF range MOBY D readers

SLG D11/SLG D11S basic unit for ANT D2 and ANT D5 antennas

Article number	6GT2698-1AC00	6GT2698-2AC00
Product type designation	SLG D11 reader	SLG D11S reader
Supply voltage, current		
consumption, power loss		
Supply voltage		
 at DC Rated value 	24 V	24 V
• at DC	20 30 V	20 30 V
Consumed current at DC at 24 V		
typical	0.2 A	0.2 A
• maximum	0.6 A	0.6 A
Permitted ambient conditions		
Ambient temperature		
 during operation 	-25 +55 °C	-25 +55 °C
 during storage 	-25 +70 °C	-25 +70 °C
 during transport 	-25 +70 °C	-25 +70 °C
Protection class IP	IP65	IP65
Shock resistance	EN 60721-3-7 Class 7 M2	EN 60721-3-7 Class 7 M2
Shock acceleration	300 m/s ²	300 m/s ²
Vibrational acceleration	15 m/s ²	15 m/s ²
Design, dimensions and weight		
Width	80 mm	80 mm
Height	40 mm	40 mm
Depth	160 mm	160 mm
Net weight	0.26 kg	0.26 kg
Mounting type	2 x M5 screws	2 x M5 screws
Cable length		
 of antenna cable minimum 	3.3 m	3.3 m
 of antenna cable maximum 	10.5 m	10.5 m
 with RS232 interface maximum 	30 m	
 for RS422 interface maximum 		300 m
Standards, specifications, approvals		
Certificate of suitability	CE, FCC, IC (Canada), UL 60950, safe for cardiac pacemakers	CE, FCC, IC (Canada), UL 60950, safe for cardiac pacemakers
MTBF	23 у	23 у
Accessories		
Accessories	Various antennas are available, Wide-range power supply, connectors and cables	Various antennas are available Wide-range power supply, connectors and cables
MOBY D readers

SLG D11/SLG D11S basic unit for ANT D2 and ANT D5 antennas

Selection and ordering data Dimensional drawings Article No. 6GT2698-1AC00 SLG D11 reader (::) \mathbf{b} 1 40 Basic unit (without antenna) 26 with RS232 serial interface for connection to PC/PLC. 6GT2698-2AC00 SLG D11S reader 12 -33+ Basic unit (without antenna) 80 with RS422 serial interface for connection to SIMATIC S7/PROFIBUS/PROFINET 日 via communication module. Accessories Ø5.5 Note: All connection options can be found in section 5. "Communication Modules". Antenna ANT D2 6GT2698-5BB00 09 For SLG D11 / SLG D11S basic units, incl. antenna cable, PVC, length 3.3 m. SIEMENS See page 2/140 Antenna ANT D5 6GT2698-5AA10 For SLG D11 / SLG D11S basic ШC 山口 units. See page 2/141. Wide-range power supply 100 V ... 240 V AC / 24 V DC, 3 A SLG D11 / SLG D11S reader - basic unit With no-load protection, with More information continuous short-circuit protection All current wireless approvals can be found on the Internet at: • With EU plug 6GT2898-0AA00 http://www.siemens.com/rfid-approvals • With UK plug 6GT2898-0AA10 • With US plug 6GT2898-0AA20 Connecting cable for 24 V DC 6GT2491-1HH50 For wide-range power supply, PUR, length 5 m. 01) 24 V connector (M12 socket) 6GT2390-1AB00 For SLG D1x reader. RS232 cable for SLG D11, PUR 5 m 6GT2691-4BH50 6GT2691-4BN20 20 m DVD "RFID-Systeme Software & 6GT2080-2AA20 Dokumentation

RFID systems for the HF range MOBY D readers

SLG D12 / SLG D12S

Overview





6GT2602-0AB00 and 6GT2602-0AB10-0AX0

Technical specifications

The SLG D12 / SLG D12S basic devices are universal readers in the medium performance range with integral antennas.

SLG D12

Equipped with RS232 serial interface for connection to PC/PLC.

SLG D12S

Equipped with an RS422 serial interface, which permits commu-nication via the communication modules ASM 456, ASM 475, SIMATIC RF120C, RF160C, RF170C and SIMATIC RF180C, or RF182C to SIMATIC S7, PROFIBUS/PROFINET or Ethernet TCP/IP.

Article number	6GT2601-0AB00	6GT2602-0AB00	6GT2602-0AB10-0AX0
Product type designation	SLG D12 reader	SLG D12S reader	SLG D12S reader
Suitability for operation	ISO 15693 transponders (MDS Dxxx), for connecting to PC systems	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules	ISO 15693 transponders (MDS Dxxx), for connecting to communication modules
Wireless frequencies			
Operating frequency Rated value	13.56 MHz	13.56 MHz	13.56 MHz
Electrical data			
Range maximum	220 mm; Range is dependent on transp http://support.automation.siemens.com	oonder type: observe /WW/view/en/67384964	
Protocol with radio transmission	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3	ISO 15693, ISO 18000-3
Transfer rate with radio transmission maximum	26.5 kbit/s	26.5 kbit/s	26.5 kbit/s
Product feature multitag-capable	Yes	No	No
Transfer rate at the point-to-point connection serial maximum	38.4 kbit/s	19.2 kbit/s	19.2 kbit/s
Transmission time for user data			
 for write access per byte typical 	2.5 ms	2.5 ms	2.5 ms
 for read access per byte typical 	2.5 ms	2.5 ms	2.5 ms
Interfaces			
Standard for interfaces for communication	RS232	RS422	RS422
Type of electrical connection	Data: Sub-D, 9-pin, male, voltage: M12, 4-pin, female connector	Data: Sub-D, 9-pin, male, voltage: M12, 4-pin, female connector	M12, 8-pin
Mechanical data			
Material	PA 12	PA 12	PA 12
Color	anthracite	anthracite	anthracite
Tightening torque of the screw for securing the equipment maximum	2 Nm	2 Nm	2 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm	0 mm
Supply voltage, current consumption, power loss			
Supply voltage			
 at DC Rated value 	24 V	24 V	24 V
• at DC	20 30 V	20 30 V	20 30 V
Consumed current at DC at 24 V			
typical	0.15 A	0.15 A	0.15 A
• maximum	0.6 A	0.6 A	0.6 A

RFID systems for the HF range MOBY D readers

			SLG D12 / SLG D12S
Article number	6GT2601-0AB00	6GT2602-0AB00	6GT2602-0AB10-0AX0
Product type designation	SLG D12 reader	SLG D12S reader	SLG D12S reader
Permitted ambient conditions			
Ambient temperature			
 during operation 	-25 +55 °C	-25 +55 °C	-25 +55 °C
 during storage 	-25 +70 °C	-25 +70 °C	-25 +70 °C
 during transport 	-25 +70 °C	-25 +70 °C	-25 +70 °C
Protection class IP	IP65	IP65	IP65
Shock resistance	EN 60721-3-7 Class 7 M2	EN 60721-3-7 Class 7 M2	EN 60721-3-7 Class 7 M2
Shock acceleration	300 m/s ²	300 m/s ²	300 m/s ²
Vibrational acceleration	15 m/s ²	15 m/s ²	15 m/s ²
Design, dimensions and weight			
Width	80 mm	80 mm	80 mm
Height	40 mm	40 mm	40 mm
Depth	160 mm	160 mm	160 mm
Net weight	0.23 kg	0.23 kg	0.23 kg
Mounting type	2 x M5 screws	2 x M5 screws	2 x M5 screws
Cable length			
 with RS232 interface maximum 	30 m		
 for RS422 interface maximum 		300 m	300 m
Standards, specifications, approvals			
Certificate of suitability	CE, FCC, IC (Canada), UL 60950, safe for cardiac pacemakers	CE, FCC, IC (Canada), UL 60950, safe for cardiac pacemakers	CE, FCC, IC (Canada), UL 60950, safe for cardiac pacemakers
MTBF	23 у	23 у	23 у
Accessories			
Accessories	Wide-range power supply, connectors, cables	Wide-range power supply, connectors, cables	Wide-range power supply, connectors, cables

Selection and ordering data

	Article No.		Article No.
SLG D12 reader	6GT2601-0AB00	Connector for reader	6GT2490-1AA00
With RS232 serial interface and integrated antenna.		IP65 degree of protection, 9-pin Sub-D connector.	
SLG D12S reader	6GT2602-0AB00		
With RS422 serial interface and integrated antenna for connection to SIMATIC S7 / PROFIBUS / PROFINET or Ethernet TCP/IP.			
SLG D12S reader, for single-cable connection	6GT2602-0AB10-0AX0		
With RS422 serial interface and		Wide-range power supply	
nector for data and voltage supply. Power supply via communication module.		Primary side: AC 100 240 V, secondary side: 24 V DC, 3 A, with no-load protection and continuous	
Connector: M12, 8-pin (male)		short-circuit protection.	
Accessories		EU connector version	6GT2898-0AA00
Note:		 UK connector version 	6GT2898-0AA10
All connection options can be found in section 5.		US connector version	6GT2898-0AA20
"Communication Modules".		Cable for wide-range power	6GT2491-1HH50
RS232 connecting cable			
Between PC and SLG D12, PUR.		24 V DC, POR, length 5 m.	
		81	
		24 V connector (M12 socket)	6GT2390-1AB00
		for SLG D1x readers	
5 m	6GT2691-4BH50		
20 m	6GT2691-4BN20		
		DVD "RFID-Systems Software & Documentation"	6GT2080-2AA20

Siemens ID 10 · 2016

2/127

MOBY D readers

SLG D12 / SLG D12S

Dimensional drawings



SLG D12 / SLG D12S reader, basic unit

More information

All current wireless approvals can be found on the Internet at: http://www.siemens.com/rfid-approvals

Overview

Note

Detailed configuration and commissioning data is contained in the "Manual for Configuration, Assembly and Service".

Transmission window

The reader generates an inductive alternating field. The field is at its strongest near the antenna and declines considerably as the distance from the antenna increases. The distribution of the field depends on the structure and geometry of the antennas in the reader and transponder.

A prerequisite for the function of the transponder is a minimum field strength at the transponder that is achieved at a distance S_g from the reader. The picture below shows the transmission window between the transponder and reader:



Traversing speed for SLG D1x / ANT Dx (with one transponder in the field)

Reader	SLG D11		SLG D12	SLG D11S		SLG D12S
Antenna	ANT D2	ANT D5		ANT D2	ANT D5	
UID number (8 bytes)	≤ 1.2	≤ 3.5	≤ 2.5	≤ 0.4	≤ 1.0	≤ 0.8
ISO transponder, e.g. MDS D100						
Read (with 4 bytes of user data / 1 block)	≤ 1.2	≤ 1.6	≤ 1.2	≤ 0.4	≤ 3.0	≤ 1.4
Write (with 4 bytes of user data / 1 block)	≤ 0.2	≤ 1.2	≤ 1.0	≤ 0.3	≤ 2.8	≤ 1.2
Read (with 112 bytes of complete user data)	≤ 0.4	≤ 1.4	≤ 0.8	≤ 0.2	≤ 2.2	≤ 1.0
Write (with 112 bytes of complete user data)	≤ 0.1	≤ 0.4	≤ 0.2	≤ 0.1	≤ 0.5	≤ 0.2

All values in the table in m/s.

Sa: Operating distance between transponder and reader

 $\rm S_g:$ Limit distance (maximum clear distance between upper surface of antenna and transponder, at which the transmission can still function under normal conditions)

L: Length of a transmission window

SP: Intersection of the axes of symmetry of the transponder

The transmittable quantity of information between reader and transponder depends on:

- the speed at which the transponder passes the antenna ("passing speed")
- Length of the inductive alternating field of the reader, through which the transponder moves ("transmission window").

Communication between reader and transponder

Communication between the reader and transponder is asynchronous.

Data transfer, reader - transponder

Read	≥ 3.5 ms/byte
Write	≥ 9.5 ms/byte (EEPROM)
Transmission time of ID number	
 SLG D12S ANT D5, ANT D6, ANT D10 	90 ms (8 bytes at 19.2 Kbit/s)
SLG D11S ANT D5	
 SLG D12 ANT D5, ANT D6, ANT D10 	60 ms (8 bytes at 38.4 Kbit/s)
SLG D11 ANT D5	

HF antennas

Introduction

Overview

Antennas	Features	Page	Antennen	Merkmale	Page
ANT 1	The ANT 1 is a universal flat antenna, also designed for dynamic applications. Usable for readers: • RF350R	2/131	ANT D1	The ANT D1 is a universal antenna for the areas of production and logistics that can also be used in dynamic applications. Usable for readers: • RF290R	2/139
ANT 3	Due to its slimline, compact design, the ANT 3 antenna can still be precisely positioned even in cramped conditions. Usable for readers: • RF250R • RF350R • RF350M	2/132	ANT D2	The ANT D2 antenna is specially designed for high speeds with a small antenna size, e.g. in over- head conveyors, assembly lines, production and order picking. The ANT D2 can be mounted directly onto metal surfaces. The antenna is designed for transponders that are directed sideways past the antenna.	2/140
ANT 3S	Due to its slimline, compact design, the ANT 3S antenna can still be precisely positioned even in cramped conditions. The ANT 3S is suitable only for use	2/133	ANT D5	Usable for readers: • SLG D11 / SLG D11S The ANT D5 is a universal antenna	2/141
	with transponders MDS D117, MDS D127, MDS D421 and MDS D521. Usable for readers: • RF250R • RF350R • RF350M			designed for warehouse, logistics and distribution applications. The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions. The antenna is designed for transponders that are directed	
ANT 8	The ANT 8 antenna is a cylindrical antenna and is intended predomi- nantly for the area of tool identifica- tion. The extremely small design	2/134		 sideways past the antenna. Usable for readers: RF290R SLG D11 / SLG D11S 	
ν.	of the antenna allows extremely accurate positioning. Usable for readers: • RF250R • RF350M		ANT D6	The ANT D6 is a universal antenna designed for warehouse, logistics and distribution applications. The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions.	2/143
ANT 12	The ANT 12 antenna is a universal round antenna in M12 design for assembly lines with extremely small workpiece holders.	2/136		Usable for readers: • RF290R	
	• RF250R • RF350R • RF350M		ANT D10	The ANT D10 is a universal antenna. It has been designed for warehouse, logistics and distribu- tion applications, and is especially suitable for the clothing industry	2/145
ANT 18	The ANT 18 antenna is a universal round antenna in M18 design for assembly lines with small workpiece holders. Usable for readers: • RF250R • RF350R • RF350M	2/137	_	and laundries. It possesses an advantageous geometry for use with small transponders and a long transmission field. The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions.	
ANT 30	The ANT 30 antenna is a universal round antenna in M30 design for assembly lines with small workpiece holders. Usable for readers: • RF250R • RF350R • RF350M	2/138		• RF290R	

HF antennas

ANT 1 for RF350R



The ANT 1 is a universal flat antenna, also designed for dynamic applications.

The dimensions are L x W x H (mm): $75 \times 75 \times 20$.

Technical specifications

Article number	6GT2398-1CB00
Product type designation	ANT 1 antenna
Suitability for operation	RF350R / MOBY E
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	M8, 4-pin
Design of plug-in connection	male
Mechanical data	
Material	PA 12
Color	Anthracite
Tightening torque of the screw for securing the equipment maximum	2 Nm
Mounting distance	
 relating to metal surfaces recommended minimum 	0.02 m
Permitted ambient conditions	
Ambient temperature	
 during operation 	-25 +70 °C
 during storage 	-40 +85 °C
 during transport 	-40 +85 °C
Protection class IP	IP67
Resistance to mechanical stress	no bending or torsion permitted
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Width	75 mm
Height	75 mm
Depth	20 mm
Net weight	225 g
Mounting type	2 screws M5
Cable length of antenna cable	3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, IC, cULus, Ex approval only together with reader 6GT2801-4AB10

Selection and ordering data

	Article No.
ANT 1 external antenna	6GT2398-1CB00
for RF350R readers. The antenna cable (3m long) is permanently connected to the antenna.	

Dimensional drawings



ANT 1 antenna

HF antennas

ANT 3 for RF250R, RF350R and RF350M

Overview





Due to its slimline, compact design, the ANT 3 antenna can still be precisely positioned even in cramped conditions. The dimensions are L x W x H (mm): $50 \times 28 \times 10$.

Technical specifications

Article number	6GT2398- 1CD30-0AX0	6GT2398- 1CD40-0AX0	
Product type designation	ANT 3 antenna	ANT 3 antenna incl. antenna cable (3 m)	
Suitability for operation	RF250R / RF350R / RF350M	RF250R / RF350R	
Wireless frequencies			
Transmission frequency Rated value	13.56 MHz		
Electrical data			
Type of electrical connection of the antenna	M8, 4-pin		
Design of plug-in connection	female	male	
Mechanical data			
Material	PA6 V0		
Color	black		
Tightening torque of the screw for securing the equipment maximum	1 Nm		
Mounting distance			
 relating to metal surfaces recommended minimum 	0 m		
Permitted ambient conditions			
Ambient temperature			
 during operation 	-25 +70 °C		
 during storage 	-40 +85 °C		
 during transport 	-40 +85 °C		
Protection class IP	IP67		
Shock resistance	according to EN 60721-3-7 Class 7M2		
Shock acceleration	500 m/s ²		
Vibrational acceleration	200 m/s ²		

Article number	6GT2398- 1CD30-0AX0	6GT2398- 1CD40-0AX0
Design, dimensions and weight		
Width	28 mm	
Height	50 mm	
Depth	10 mm	
Net weight	35 g	160 g
Mounting type	2 x M4 screws	2 x M4 screws
Cable length of antenna cable	-	3 m
Standards, specifications, approvals		
Certificate of suitability	CE, FCC, IC, cULus	
Accessories	Antenna cable	Included: 6GT23910-AH30 (antenna cable)

Selection and ordering data

	Article No.
ANT 3 external antenna	
Without antenna connecting cable	6GT2398-1CD30-0AX0
For RF250R, RF350R and RF350M readers.	
• With antenna connecting cable included in the scope of delivery; can be connected at both ends (connector M8 straight / M8 angled), length 3 m.	6GT2398-1CD40-0AX0
For RF250R and RF350R readers.	
Accessories	
Antenna connecting cable for ANT 3 / ANT 3S / ANT 8	
For direct connection of ANT 3, ANT 3S and ANT 8 to RF350M	
 Length 0.1 m (figure see page 2/119) 	6GT2898-0EA00
• Lenath 3 m	6GT2391-0AH30

Dimensional drawings



ANT 3 antenna

HF antennas

ANT 3S for RF250R, RF350R and RF350M





Due to its slimline, compact design, the ANT 3S antenna can still be precisely positioned even in cramped conditions.

The ANT 3S is suitable only for use with transponders MDS D117, MDS D127, MDS D421 and MDS D521.

The dimensions of the antenna are L x W x H (mm): 50 x 28 x 10.

Technical specifications

Article number	6GT2398- 1CD50-0AX0	6GT2398- 1CD60-0AX0
Product type designation	ANT 3S antenna	ANT 3S antenna including antenna cable (3 m)
Suitability for operation	RF250R / RF350R / RF350M	RF250R / RF350R
Wireless frequencies		
Transmission frequency Rated value	13.56 MHz	
Electrical data		
Type of electrical connection of the antenna	M8, 4-pin	
Design of plug-in connection	female	male
Mechanical data		
Material	PA6 V0	
Color	black	
Tightening torque of the screw for securing the equipment maximum	1 Nm	
Mounting distance		
 relating to metal surfaces recommended minimum 	0 m	
Permitted ambient conditions		
Ambient temperature		
 during operation 	-25 +70 °C	
 during storage 	-40 +85 °C	
 during transport 	-40 +85 °C	
Protection class IP	IP67	
Shock resistance	according to EN 6 Class 7M2	0721-3-7
Shock acceleration	500 m/s ²	
Vibrational acceleration	200 m/s ²	

Article number	6GT2398- 1CD50-0AX0	6GT2398- 1CD60-0AX0
Design, dimensions and weight		
Width	28 mm	
Height	50 mm	
Depth	10 mm	
Net weight	35 g	160 g
Mounting type	2 x M4 screws	2 x M4 screws
Cable length of antenna cable	-	3 m
Standards, specifications, approvals		
Certificate of suitability	CE, FCC, IC, cUL	JS
Accessories	Antenna cable	Included: 6GT23910-AH30 (antenna cable)

Selection and ordering data

	Article No.
ANT 3S external antenna	
 Without antenna connecting cable For RF250R, RF350R and RF350M readers. 	6GT2398-1CD50-0AX0
 With antenna connecting cable included in the scope of delivery; can be connected at both ends (connector M8 straight / M8 angled), length 3 m. 	6GT2398-1CD60-0AX0
For RF250R and RF350R readers.	
Accessories	
Antenna connecting cable for ANT 3 / ANT 3S / ANT 8	
For direct connection of ANT 3, ANT 3S and ANT 8 to RF350M (6GT2803-1BA10).	

6GT2898-0EA00

6GT2391-0AH30

- Length 0.1 m (figure see page 2/119)
- Length 3 m

Dimensional drawings



ANT 3S antenna

HF antennas

Overview



The ANT 8 antenna is a cylindrical antenna and is intended predominantly for the area of tool identification. The extremely small design of the antenna allows extremely accurate positioning. Dimensions $\emptyset \times L$ (mm): M8 x 38.



Technical specifications

Article number	6GT2398-1CF00	6GT2398-1CF10
Product type designation	ANT 8 antenna	ANT 8 antenna incl. antenna cable
Suitability for operation	RF250R / RF350M	RF250R
Wireless frequencies		
Transmission frequency Rated value	13.56 MHz	13.56 MHz
Electrical data		
Type of electrical connection of the antenna	M8, 4-pin	M8, 4-pin
Design of plug-in connection	female	male
Mechanical data		
Material	Stainless steel V2A	Stainless steel V2A
Color	Silver	Silver
Tightening torque of the screw for securing the equipment maximum	3 Nm	3 Nm
Mounting distance		
 relating to metal surfaces recommended minimum 	0 m	0 m
Permitted ambient conditions		
Ambient temperature		
 during operation 	-25 +70 °C	-25 +70 °C
 during storage 	-40 +85 °C	-40 +85 °C
 during transport 	-40 +85 °C	-40 +85 °C
Protection class IP	IP67, front	IP67, front
Shock resistance	according to EN 60721-3-7 Class 7M2	according to EN 60721-3-7 Class 7M2
Shock acceleration	500 m/s ²	500 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Depth	40 mm	40 mm
Diameter	8 mm	8 mm
Net weight	10 g	140 g
Mounting type	2 stainless steel csrew nuts M8 x 1.0 (included)	2 stainless steel csrew nuts M8 x 1.0 (included)
Cable length of antenna cable		3 m
Standards, specifications, approvals		
Certificate of suitability	CE, FCC, IC, cULus	CE, FCC, IC, cULus
Accessories		
Accessories	Antenna cable	Included: 6GT23910-AH30 (antenna cable, length 3 m)

RFID systems for the HF range HF antennas

ANT 8 for RF250R and RF350M

Selection and ordering data		Dimensional drawin	gs	
	Article No.			
ANT 8 external antenna				
• Without antenna connecting cable For RF250R and RF350M readers.	6GT2398-1CF00	M8	M8x1m	<u>im</u>
• With antenna connecting cable. The antenna connecting cable is included in the scope of delivery of the antenna and can be con- nected at both ends (M8 connec- tor straight / M8 angled). Length 3 m.	6GT2398-1CF10	5W 13		
For RF250R readers.				
Accessories				
Antenna connecting cable for ANT 3 / ANT 3S / ANT 8				01142
For direct connection of ANT 3, ANT 3S and ANT 8 to RF350M (6GT2803-1BA10).				FS10_XX_0
• Length 0.1 m	6GT2898-0EA00			ര്
30		ANT 8 antenna		
• Length 3 m	6GT2391-0AH30			

HF antennas

ANT 12 for RF250R, RF350R and RF350M

Overview





The ANT 12 antenna is a universal round antenna in M12 design for assembly lines with extremely small workpiece holders. Dimensions $\emptyset \times L$ (mm): M12 \times 40.

Technical specifications

Article number	6GT2398-1CC00
Product type designation	ANT 12 antenna
Suitability for operation	RF250R / RF350R / RF350M / MOBY E
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	M8, 4-pin
Design of plug-in connection	male
Mechanical data	
Material	Crastin
Color	Pastel turquoise
Tightening torque of the screw for securing the equipment maximum	3 Nm
Mounting distance	
 relating to metal surfaces recommended minimum 	0 m

Article number	6GT2398-1CC00
Product type designation	ANT 12 antenna
Permitted ambient conditions	
Ambient temperature	
 during operation 	-25 +70 °C
 during storage 	-40 +85 °C
 during transport 	-40 +85 °C
Protection class IP	IP67, front
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Depth	40 mm
Diameter	12 mm
Net weight	145 g
Mounting type	2 plastic csrew nuts M12 x 1.0
Cable length of antenna cable	3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, IC, cULus, Ex approval only together with RF350R reader 6GT2801-4AB10

Selection and ordering data

	Article No.
ANT 12 external antenna	6GT2398-1CC00
for readers RF250R, RF350R and RF350M.	

Dimensional drawings



ANT 12 antenna

RFID systems for the HF range HF antennas

ANT 18 for RF250R, RF350R and RF350M





The ANT 18 antenna is a universal round antenna in M18 design for assembly lines with small workpiece holders. Dimensions \emptyset x L (mm): M18 x 55.

Technical specifications

6GT2398-1CA00
ANT 18 antenna
RF250R / RF350R / RF350M / MOBY E
13.56 MHz
M8, 4-pin
male
male
male Crastin
male Crastin Pastel turquoise
male Crastin Pastel turquoise 3 Nm
male Crastin Pastel turquoise 3 Nm

Article number	6GT2398-1CA00
Product type designation	ANT 18 antenna
Permitted ambient conditions	
Ambient temperature	
 during operation 	-25 +70 °C
 during storage 	-40 +85 °C
 during transport 	-40 +85 °C
Protection class IP	IP67, front
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Depth	55 mm
Diameter	18 mm
Net weight	130 g
Mounting type	2 plastic csrew nuts M18 x 1.0
Cable length of antenna cable	3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, IC, cULus, Ex approval only together with RF350R reader 6GT2801-4AB10

Selection and ordering data

	Article No.
ANT 18 external antenna	6GT2398-1CA00
for readers RF250R, RF350R and RF350M.	

Dimensional drawings



ANT 18 antenna

HF antennas

ANT 30 for RF250R, RF350R and RF350M

Overview



The ANT 30 antenna is a universal round antenna in M30 design for assembly lines with small workpiece holders. Dimensions Ø x L (mm): M30 x 58

Technical specifications

Article number	6GT2398-1CD00
Product type designation	ANT 30 antenna
Suitability for operation	RF250R / RF350R / RF350M / MOBY E
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	M8, 4-pin
Design of plug-in connection	male
Design of plug-in connection Mechanical data	male
Design of plug-in connection Mechanical data Material	male Crastin
Design of plug-in connection Mechanical data Material Color	male Crastin Pastel turquoise
Design of plug-in connection Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum	male Crastin Pastel turquoise 3 Nm
Design of plug-in connection Mechanical data Material Color Tightening torque of the screw for securing the equipment maximum Mounting distance	male Crastin Pastel turquoise 3 Nm

6GT2398-1CD00 ANT 30 antenna
ANT 30 antenna
-25 +70 °C
-40 +85 °C
-40 +85 °C
IP67, front
according to EN 60721-3-7 Class 7M2
500 m/s ²
200 m/s ²
58 mm
30 mm
180 g
2 plastic csrew nuts M30 x 1.5
3 m
CE, FCC, IC, cULus, Ex approval only together with RF350R reader 6GT2801-4AB10

Selection and ordering data

	Article No.
ANT 30 external antenna	6GT2398-1CD00
for readers RF250R, RF350R and RF350M.	

Dimensional drawings



ANT 30 antenna

HF antennas



small

The ANT D1 is a universal antenna for the areas of production and logistics that can also be used in dynamic applications. The high degree of protection (IP67) means the antenna can also be used under harsh industrial conditions.

Technical specifications	
Article number	6GT2698-5AC00
Product type designation	ANT D1 antenna
Suitability for operation	RF290R
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	1-pol. TNC-Stecker
Design of plug-in connection	female
Mechanical data	
Material	PA 12
Color	Anthracite
Mounting distance	
 relating to metal surfaces recommended minimum 	0.02 m
Permitted ambient conditions	
Ambient temperature	
 during operation 	-20 +55 °C
 during storage 	-25 +70 °C
 during transport 	-25 +70 °C
Protection class IP	IP67
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²
Design, dimensions and weight	
Width	75 mm
Height	75 mm
Depth	20 mm
Net weight	270 g
Mounting type	2 screws M5
Cable length of antenna cable	3.3 m
Accessories	Antenna cable

Selection and ordering data

	Article No.
ANT D1 antenna	6GT2698-5AC00
For RF290R readers, including antenna cable, PVC, length 3.3 m	
Accessories	
Cable extension	6GT2691-0DH72
Length 7.2 m	

Dimensional drawings



ANT D1 antenna

HF antennas

Overview



The ANT D2 antenna is designed for transponders that are directed sideways past the antenna. This antenna is specially designed for high speeds with a small antenna size, e.g. in overhead conveyors, assembly lines, production and order picking. It can be mounted directly onto metal surfaces.

Technical specifications

Article number	6GT2608-5BB00
Product type designation	
	MORY D with SLC D11
	MOBT D WILLISEG DTT
Transmission frequencies	12 56 MU7
	13.56 MHZ
antenna	1-pol. INC-Stecker
Design of plug-in connection	female
Mechanical data	
Material	PA 12
Color	Anthracite
Tightening torque of the screw for securing the equipment maximum	2 Nm
Mounting distance	
 relating to metal surfaces recommended minimum 	0 m
Permitted ambient conditions	
Ambient temperature	
 during operation 	-25 +70 °C
 during storage 	-40 +85 °C
 during transport 	-40 +85 °C
Protection class IP	IP65
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	500 m/s ²
Vibrational acceleration	100 m/s ²
Design, dimensions and weight	
Width	75 mm
Height	75 mm
Depth	40 mm
Net weight	260 g
Mounting type	2 screws M5, mounting dependent on direction
Cable length of antenna cable	3.3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, IC, cULus

Selection and ordering data

	Article No.
ANT D2 antenna	6GT2698-5BB00
For SLG D11 / SLG D11S basic units, lateral antenna field, incl. PVC antenna cable (length 3,3 m).	

Dimensional drawings





G_FS10_XX_00205



ANT D2 antenna

RFID systems for the HF range HF antennas

ANT D5 for RF290R and SLG D11 / D11S





The ANT D5 is a universal antenna designed for warehouse, logistics and distribution applications. The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions. The antenna is designed for transponders that are directed sideways past the antenna.

Technical specifications

Article number	6GT2698-5AA10
Product type designation	ANT D5 antenna
Suitability for operation	RF290R, MOBY D with SLG D10, D11
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	1-pol. TNC-Stecker
Design of plug-in connection	female
Mechanical data	
Material	Aluminum/plastic
Color	black/gray
Mounting distance	
 relating to metal surfaces recommended minimum 	0 m
Permitted ambient conditions	
Ambient temperature	
 during operation 	-20 +55 °C
 during storage 	-25 +70 °C
 during transport 	-25 +70 °C
Protection class IP	IP65
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	300 m/s ²
Vibrational acceleration	10 m/s ²

Article number	6GT2698-5AA10
Product type designation	ANT D5 antenna
Design, dimensions and weight	
Width	380 mm
Height	380 mm
Depth	110 mm
Net weight	2 kg
Mounting type	4 screws M6
Cable length of antenna cable	3.3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC
Accessories	Antenna cables 3.3 m, 10 m, extension 7.2 m

Selection and ordering data

	Article No.
ANT D5 antenna	6GT2698-5AA10
for RF290R readers and SLG D11 / SLG D11S basic units, including antenna cable, PVC, length 3.3 m	
Accessories	
Antenna switch	6GT2690-0AC00
For connecting several antennas (ANT D5 or ANT D6) to one RF290R reader, IP65, -25 °C to +65 °C	
C	
SIMATIC RF260X antenna multiplexer	6GT2894-0EA00
Antenna multiplexer for RF290R reader when connected via RS232.	
6 x antenna outputs (for ANT D5, ANT D6 and ANT D10); IP65; 240 mm x 150 mm x 70 mm; including antenna connecting cable, cable length 0.4 m.	
Accessories for antenna switch and antenna multiplexer	
Antenna connecting cable	
Between antenna and reader or antenna switch/multiplexer, PVC material.	
• Length 3.3 m	6GT2691-0CH33
Length 10 m	6GT2691-0CN10
Extension cable	6GT2691-0DH72
For 6GT2691-0CH33, PVC material. Length 7.2 m.	

HF antennas

ANT D5 for RF290R and SLG D11 / D11S

Dimensional drawings



ANT D5 antenna

_

RFID systems for the HF range

HF antennas





The ANT D6 is a universal antenna designed for warehouse, logistics and distribution applications. The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions.

Technical specifications

Article number	6GT2698-5AB00
Product type designation	ANT D6 antenna
Suitability for operation	RF290R, MOBY D with SLG D10
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	1-pol. TNC-Stecker
Design of plug-in connection	female
Mechanical data	
Material	Aluminum/plastic
Color	gray / black
Mounting distance	
 relating to metal surfaces recommended minimum 	0 m
Permitted ambient conditions	
Ambient temperature	
 during operation 	-20 +55 °C
 during storage 	-25 +70 °C
 during transport 	-25 +70 °C
Protection class IP	IP65
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	300 m/s ²
Vibrational acceleration	10 m/s ²
Design, dimensions and weight	
Width	480 mm
Height	580 mm
Depth	110 mm
Net weight	3.3 kg
Mounting type	4 screws M6
Cable length of antenna cable	3.3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, cULus
Accessories	
Accessories	Antenna cables 3.3 m, 10 m, extension 7.2 m

Selection and ordering data

	Article No.
ANT D6 antenna	6GT2698-5AB00
for RF290R readers, including antenna cable, PVC, length 3.3 m	
Accessories	
Shrouding cover	6GT2690-0AD00
Serves as contact protection for ANT D6	
Antenna switch	6GT2690-0AC00
For connecting several antennas (ANT D5 or ANT D6) to one RF290R reader, IP65, -25 °C to +65 °C	
Hard S Hard S	
SIMATIC RF260X antenna multiplexer	6GT2894-0EA00
Antenna multiplexer for RF290R reader when connected via RS232.	
6 x antenna outputs (for ANT D5, ANT D6 and ANT D10); IP65; 240 mm x 150 mm x 70 mm; including antenna connecting cable, cable length 0.4 m.	
Accessories for antenna switch and antenna multiplexer	
Antenna connecting cable	
Between antenna and reader or antenna switch/multiplexer, PVC material.	
• Length 3.3 m	6GT2691-0CH33
Length 10 m	6GT2691-0CN10
Extension cable	6GT2691-0DH72

For 6GT2691-0CH33, PVC material. Length 7.2 m.

HF antennas

ANT D6 for RF290R

Dimensional drawings



ANT D6 antenna

HF antennas

ANT D10 for RF290R

Overview





The ANT D10 is a universal antenna designed for warehouse, logistics and distribution applications. The high degree of protection (IP65) enables the antenna to be used under harsh industrial conditions.

Technical specifications	
Article number	6GT2698-5AF00
Product type designation	ANT D10 antenna
Suitability for operation	RF290R, MOBY D with SLG D10
Wireless frequencies	
Transmission frequency Rated value	13.56 MHz
Electrical data	
Type of electrical connection of the antenna	1-pol. TNC-Stecker
Design of plug-in connection	female
Mechanical data	
Material	Aluminum/plastic
Color	Transparent (cover), gray/black (antenna)
Mounting distance	
 relating to metal surfaces recommended minimum 	0 m
Permitted ambient conditions	
Ambient temperature	
 during operation 	-20 +55 °C
 during storage 	-25 +70 °C
 during transport 	-25 +70 °C
Protection class IP	IP65
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	300 m/s ²
Vibrational acceleration	10 m/s ²
Design, dimensions and weight	
Width	365 mm
Height	1 150 mm
Depth	115 mm
Net weight	10 kg
Mounting type	4 screws M6
Cable length of antenna cable	3.3 m
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, cULus
Accessories	
Accessories	Antenna cables 3.3 m, 10 m, extension 7.2 m

HF antennas

Selection and ordering data

Dimensional drawings

	Article No.
ANT D10 antenna	6GT2698-5AF00
For the RF290R reader, incl. antenna cable, PVC, length 3.3 m.	
Accessories	
Antenna switch	6GT2690-0AC00
For connecting multiple antennas (ANT D5, ANT D6 or ANT D10) to one reader	
SIMATIC RF260X antenna multiplexer	6GT2894-0EA00
Antenna multiplexer for RF290R reader when connected via RS232.	
6 x antenna outputs (for ANT D5, ANT D6 and ANT D10); IP65; 240 mm x 150 mm x 70 mm; including antenna connecting cable, cable length 0.4 m	
Accessories for antenna switch and antenna multiplexer	
Antenna connecting cable	
Between antenna and reader or antenna switch/multiplexer, PVC material.	
• Length 3.3 m	6GT2691-0CH33
• Length 10 m	6GT2691-0CN10
Extension cable	6GT2691-0DH72

For 6GT2691-0CH33, PVC material. Length 7.2 m.



ANT D10 antenna





3/2	RF600
3/4	RF600 transponders
3/5	RF622L
3/6	RF630L
3/9	RF640L
3/11	RF680L
3/12	RF690L
3/14	RF610T
3/16	RF620T
3/18	RF622T
3/20	RF625T
3/22	RF630T
3/24	RF640T
3/26	RF680T
3/28	RF600 readers
3/29	Web-based interface
3/30	RF650R
3/33	RF680R
3/37	RF685R
3/41	RF650M mobile handheld terminal
3/44	RF600 antennas
3/45	RF620A
3/48	RF640A, RF642A

51 RF660A

RFID systems for the UHF range SIMATIC RF600

Overview



Identification tasks in the UHF range (865 to 868 MHz, 902 to 928 MHz, and 920 to 925 MHz) that demand a wide range of several meters are implemented with SIMATIC RF600. The system is suitable for storing and recording a unique identification according to the EPCglobal standard (Electronic Product Code) on products, containers or transport units. Storage of additional, freely-definable user data is also possible.

Various data carriers - from low-cost SmartLabels through to heat-resistant transponders that can be used for several thousand cycles - are available for industrial applications.

SIMATIC RF600 can be used with SIMATIC controllers and PC/IT systems.

Benefits

Designed for Industry get

SIMATIC RF600 has been specially developed for the requirements of industry. It enables economical and reliable use of RFID in production, materials management and logistics.

- Cost savings and improvement in process quality through application of UHF RFID with maximum reliability in the industrial environment:
- Application of a uniform RFID system throughout the entire production process and supplier chain as a result of inexpensive transponders and wide ranges (no technology gaps).
- Maximum availability even in applications with a complex radio environment such as high reader density, strongly reflecting metal environments, dynamic surroundings.
- Permanent RFID identification of products thanks to disposable transponders matched to the application, e.g. heat-resistant, high degree of protection.
- Wide transponder portfolio and customized versions for cost-optimized use.
- Flexibility due to compact designs and remote antennas.
- Safe and selective individual acquisition or bulk identification is possible.
- High reading speed: Even fast-moving transponders are reliably detected.

- Simplified engineering, commissioning, diagnostics and maintenance through seamless integration into Totally Integrated Automation (TIA):
- Integrated bus connection to an automation system, such as SIMATIC, SIMOTION or SINUMERIK via communication modules with PROFIBUS and PROFINET.
- Direct interfacing to IT systems via Ethernet.
- Integrated processing logic allows data preprocessing in the reader and saves costs for external PCs, software modules, etc
- Simple S7 software integration via ready-to-use function blocks.
- Extensive diagnostic functions.
- · High degree of investment protection thanks to
 - Open standards EPCglobal Class 1 Gen 2 / ISO 18000-6C or ISO 18000-6B.
 - Software compatibility between the RFID systems of Siemens.
 - Standardized communication interfaces.
 - Openness through connection possibilities to various bus systems from different manufacturers and PC environments via communication modules.
- Worldwide service and support.
 - Tried and tested in numerous customer projects.

Application

SIMATIC RF600 is used for the contactless identification of every kind of object, e.g. transport containers, pallets, production goods, or it can be used generally for recording goods in bulk. As a rule, these applications are open loops in which passive SmartLabels on goods, products, bulk containers or transport units are used. In this case, the system distinguishes itself due to its high reading speeds, large data transmission rates and the fact that it can handle long reading distances.

In addition, the system is suitable for reading and writing reusable transponders that are used in closed loops.

Typical applications include:

- Acquisition of deliveries in the incoming goods / outgoing goods departments.
- Identification of transport containers, barrels or containers at important stations in the process; creation of a "Container passport" for automatic creation of a usage history.
- Control of material flow and production in multi-variant, order-related production.
- Labeling of products under severe ambient conditions, e.g. dust, dirt, high temperatures.
- Stock monitoring and usage monitoring of tools and devices.
- Automation of warehouses and distribution centers with industrial trucks.

RFID systems for the UHF range SIMATIC RF600

Introduction

Design

The SIMATIC RF600 readers are available as variants with an integral antenna (RF685R) and with connection options for external antennas (RF650R, RF680R).

For quick and easy cabling, pre-assembled cables are available in various lengths.

Multicolored LEDs indicate the status of reader and transponder.

The high IP65 degree of protection of the reader enables it to be used in harsh industrial environments.

The SIMATIC RF600 series of transponders are used as mobile data carriers.

Transponders suitable for a wide variety of different requirements can be selected from an extensive range: For example, low-cost, heat-resistant SmartLabels for temperatures up to 230 °C, in rugged credit card format, or screw-fit transponders that can be attached by robots.

The transponders are attached to the object to be identified, e.g. by means of screws, adhesive or pre-assembled spacer.

Function

All SIMATIC RF600 readers are suitable for reliable writing and reading tasks in the UHF range from 865 to 868 MHz (ETSI), 902 to 928 MHz (FCC), and 920 to 925 MHz (CMIIT), with very large ranges up to 8 m.

The SIMATIC RF680R/685R readers are particularly suitable for use in production environments where a high protection class and integration into SIMATIC controllers are required. These two new readers also offer an extensive toolset for commissioning and diagnostics.

User-friendly function blocks simplify programming in Step 7 or the TIA Portal. Special functions are available in areas hostile to wireless communication encountered in production environments, such as reflections and dead zones resulting from metal or superimposed radio fields due to a high reader density.

In this manner, process stability is substantially increased by automatic adaptation of the transmit power and intelligent filtering of the reading results. The multi-stage filter concept ensures that, based on the wireless properties, the correct transponder within the RF field of the reader is always processed. The appropriate data storage medium is automatically selected on the basis of various indicators, such as the evaluation of the RSSI value (Received Signal Strength Indicator), the reading frequency, or the transmit power required.

Transponders that have already been processed can be stored in a "blacklist" in the reader and thus filtered out. Various mechanisms can be activated according to requirements.

One special feature of the RF685R is the integrated adaptive antenna. Whether linear (horizontal/vertical), circular or automatic polarization, the integrated antenna of the RF685R achieves the best reading rates, even in difficult radio reception environments.

The RF650R and RF680R/685R readers can be set and diagnosed by means of a Web browser. The RF680R/685R can also optionally be commissioned and diagnosed in the TIA Portal. The RF650R reader is used mainly in logistics applications where a high degree of protection and SIMATIC integration are of lesser importance. With its four external antenna connections, as many as four individual reading stations or large gate applications can be implemented. The integrated processing logic allows comprehensive filter functions and control of the digital inputs/outputs in the reader itself. Configuration, commissioning and diagnostics are easily possible by means of a web browser, without the need for installing additional software.

External sensor technology (e.g. light barriers or motion detectors) and indicator lamps or acoustic sensors are integrated by means of the four digital inputs and outputs.

Integration

A wide range of communication modules, function blocks, as well as high-performance drivers and function libraries enable easy and quick integration into user applications.

In PC/IT environments, the RF650R, RF680R and RF685R devices can be integrated by means of a simple XML protocol. Programming examples are available for this purpose.

Because the RF680R and RF685R readers are part of Totally Integrated Automation (TIA), integration into automation systems such as SIMATIC S7 is Plug & Play. The device information is contained as standard in the TIA Portal as from V13 SP1, in the same way as the easy-to-operate Identification Profile function blocks.

SIMATIC Ident Configuration Guide

Here is a compact configuration tool for setting up RFID systems:

http://support.automation.siemens.com/WW/view/en/67384964

Technical specifications

RFID system	SIMATIC RF600
Transmission frequency	865 868 MHz (ETSI) 902 928 MHz (FCC) 920 925 MHz (CMIIT)
Range	Max. 8 m
Protocol (air interface)	EPCglobal Class 1 Gen 2
	• ISO 18000-6B
	• ISO 18000-6C
Approvals	• ETSI EN 302208, CE
	• FCC
	• UL
	• CMIIT
Memory capacity	Max. 496 bits EPC, 3 424 bytes user memory
Data transfer rate for wireless transmission	Max. 300 kbps
Multitag/Bulk capability	Yes
Special features	SIMATIC or PC/IT integration
	 Configurable data processing in the readers
	 Special antennas for industrial applications
	 Powerful diagnostics functions

SIMATIC RF600 transponders

Introduction

Overview

SIMATIC RF600 offers a variety of transponders for numerous applications. All transponders are designed to be passive and maintenance-free and thus ensure problem-free operation.

The transponders support the EPCglobal Class 1, Gen 2 / ISO 18000-6C standard, and can be used with all SIMATIC RF600 readers.

Transponder	Features	Page
RF622L	Large memory UHF SmartLabel with 4 KB FRAM.	3/5
RF630L	SmartLabel based on UHF Class 1 Gen 2 technology. This SmartLabel is available in several versions.	3/6
RF640L	The SIMATIC RF640L (on-metal label) is designed for direct mounting on metal surfaces and has a read range of up to 4 m.	3/9
RF680L	Heat-resistant UHF SmartLabel for identifying objects with high temperature requirements.	3/11
RF690L	Heat-resistant UHF SmartLabel for mounting directly on metal.	3/12
RF610T SIEMENS REGIOT	A flexible card in ISO format that is suitable for a wide variety of applications, e.g. for identification of containers, pallets, or vessels. The SIMATIC RF610T can be attached to the most diverse materials, including plastic, wood, glass and metal (with spacer).	3/14
RF620T	The RF620T container transponder is suitable for identifying transport containers or pallets. It can be attached to metal if spacers are used.	3/16
RF622T	Large memory RF622T transponder with large 4 KB FRAM memory enables the storage of larger volumes of data. It is therefore especially suited to use in distributed configurations.	3/18
RF625T	also be mounted on metal surfaces. The RF625T disk transponder is suitable for use in industrial	3/20
SIEMENS SIMATIC O RF625T 6GT2810-2EE00	environments, such as in the equipping of tools, machines and plants.	

Transponder	Features	Page
RF630T SIEMENS GGT2810-25C00 SIMATIC RF630T	The RF630T screw transponder (M6) is particularly suitable for controlling and monitoring production processes.	3/22
RF640T	The RF640T tool transponder can be mounted directly on metal, and is therefore particularly suitable for tracking tools, containers and metallic equipment.	3/24
RF680T	High-temperature transponder up to 220 °C and high degree of protection IP68/IPx9K. It is suitable for industrial applica- tions with high thermal stress.	3/26
Benefits		
g eget	Designed for Indu	ustry
The comprehensiv with long ranges a appropriate solutio production:	ve portfolio of SIMATIC RF600 trans according to EPCglobal standard of on for every requirement in logistics	ponders fers the and
 Low-cost Smart 	Labels and transponders.	
 Heat-resistant S temperature ran 	martLabels and transponders for h iges up to 230 °C for use in paint sh	igh 10ps.

- Screw-fit transponders for automatic attachment by robots.
- · Screw-fit transponders for flush-mounting in metal for identifying workpieces or workpiece holders.
- Rugged transponders with high resistance to environmental influences.
- Customized solutions for SmartLabels and transponders ٠ on request.

Technical specifications

Field data (operating/limit distance) of transponders and readers (all specifications in mm)

The field data of the RF600 UHF transponders in connection with RF600 readers is listed in the technical specifications of the RFID overview.

The listed technical data are typical values and are valid at operating temperature.

SIMATIC RF600 transponders

RF6<u>22L</u>

Overview





With a capacity of 4 KB FRAM, of which 3 424 bytes are available as user memory, the new RF622L UHF RFID SmartLabel enables larger volumes of data to be stored on tagged objects, as well as facilitating rapid access to them.

The large memory label offers a considerable reading range of up to 3 meters on non-metallic surfaces.

The RF622L SmartLabel is suitable for the permanent marking of products and can be individually printed from the roll, for example with plain text or additional optical codes.

Industrial plant management, RFID identification of tools, containers and non-metallic equipment. Suitable for a host of uses in a wide range of applications, e.g. logistics.

Technical specifications

Article number	6GT2810-4AC80
Product type designation	RF622L transponder
Suitability for operation	RF600
Wireless frequencies	
Operating frequency	860 960 MHz
Electrical data	
Range maximum	3 m; observe system manual RF600: overrange is possible, range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6C
Transfer rate with radio transmission maximum	320 kbit/s
Product feature multitag-capable	Yes
Polarization	Linear
Product component Backup battery	No

Article number	6GT2810-4AC80
Product type designation	RE622L transponder
Suitability for operation	RF600
Memory	
Type of memory	FRAM
Storage capacity of the user memory	3 424 byte
Type of memory organization	EPC memory 496 bits, user memory 3 424 bytes, TID memory 32 bytes
Number of read cycles at ambient temperature < 40 °C maximum	10 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	10 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	lock, unlock, write protection, password protection
Type of transponder chip used	Fujitsu MB97R803
Mechanical data	
Material	PET
Color	white
Mounting distance relating to metal surfaces recommended minimum	5 mm
Permitted ambient conditions	
Ambient temperature	
during read/write access	-20 +85 °C
outside the read/write area	-40 +85 °C
during storage	13 23 °C
Protection class IP	IP64, in glued condition
Resistance to mechanical stress	lorsion and bending stress conditionally permissible
Design, dimensions and weight	
Width	90 mm
Height	0.5 mm
Depth	18 mm
Net weight	1 g
Mounting type	one-side adhesible
Product properties, functions, components general	
Product feature	
silicon-free	Yes
printable	Yes
Printing process	Thermal transfer process

Selection and ordering data

	Article No.
SIMATIC RF622L SmartLabel	6GT2810-2AC80
Frequency: 860 to 960 MHz, EPC: 496 bits, user memory: 3 424 bytes	
Plastic, self-adhesive, dimensions (mm): 90 x 18 x 0.5, order quantity 500 units (supplied on rolls) or a multiple thereof.	

SIMATIC RF600 transponders

RF630L

Overview









6GT2810-2AB02-0AX0

6GT2810-2AB00









6GT2810-2AB03

6GT2810-2AB01



ISO

6GT2810-2AE81-0AX1

The SIMATIC RF630L SmartLabels are suitable for (permanent) identification of products or shipping units with the Electronic Product Code (EPC) as well as with other user data. Thanks to its broadband design, the SIMATIC RF630L SmartLabel can be used in numerous countries.

RF630L

Article number	6GT2810-2AB00	6GT2810-2AB01	6GT2810-2AE81- 0AX1	6GT2810-2AB02- 0AX0	6GT2810-2AB03
Product type designation	RF630L transponder	RF630L transponder	RF630L transponder	RF630L transponder	RF630L transponder
Suitability for operation	RF600	RF600	RF600	RF600	RF600
Wireless frequencies					
Operating frequency	860 960 MHz	860 960 MHz	860 960 MHz	860 960 MHz	860 960 MHz
Electrical data					
Range maximum	8 m; observe system manual RF600: overrange is possible, range is reader dependent: observe	8 m; observe system manual RF600: overrange is possible, range is reader dependent: observe	4 m; observe system manual RF600: overrange is possible, range is reader dependent: observe	8 m; observe system manual RF600: overrange is possible, range is reader dependent: observe	5 m; observe system manual RF600: overrange is possible, range is reader dependent: observe
	http://support.automati	on.siemens.com/WW/vie	ew/en/67384964		
Protocol with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6C	EPCglobal Class 1 Gen 2 / ISO 18000-6C	EPCglobal Class 1 Gen 2 / ISO 18000-6C	EPCglobal Class 1 Gen 2 / ISO 18000-6C	EPCglobal Class 1 Gen 2 / ISO 18000-6C
Transfer rate with radio transmission maximum	320 kbit/s	320 kbit/s	320 kbit/s	320 kbit/s	320 kbit/s
Product feature multitag-capable	Yes	Yes	Yes	Yes	Yes
Polarization	Linear	Linear	Linear	Linear	Linear
Product component Backup battery	No	No	No	No	No
Memory					
Type of memory	EEPROM	EEPROM	EEPROM	EEPROM	EEPROM
Storage capacity of the user memory	12 byte	12 byte	16 byte	64 byte	64 byte
Type of memory organization	EPC memory 96 bits, TID memory 4 bytes	EPC memory 96 bits, TID memory 4 bytes	EPC memory 128 bits, TID memory 8 bytes	EPC memory 96/128 bits, user memory 64 bytes (512 bits), TID memory 4 bytes	EPC memory 96/240 bits, user memory 64 bytes (512 bits), TID memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000	100 000 000 000 000	100 000 000 000 000	100 000 000 000 000	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	100 000	100 000	100 000	100 000	100 000
Data retention time at ambient temperature < 40 °C not less than	10 у	10 y	30 у	10 y	10 y
Property of memory	lock, unlock, kill, write protection, pass- word protection	lock, unlock, kill, write protection, pass- word protection	lock, unlock, kill, write protection, pass- word protection	lock, unlock, kill, write protection, pass- word protection	lock, unlock, kill, write protection, pass- word protection
lype of transponder chip used	IMPINJ MONZA 2	IMPINJ MONZA 2	NXP G2iL	IMPINJ MONZA 4Q1	NXP G2XM
Mechanical data	R	D	DET	DET	DET
Material	Paper	Paper	PEI	PEI	PEI
Color	white	white	white	transparent	transparent
surfaces recommended minimum	3 mm	3 mm	3 mm	3 mm	3 mm
Permitted ambient conditions					
Ambient temperature					
 during read/write access 	-40 +65 °C	-40 +65 °C	-25 +85 °C	-40 +65 °C	-40 +65 °C
 outside the read/write area 	-40 +80 °C	-40 +80 °C	-40 +160 °C	-40 +80 °C	-40 +80 °C
 during storage 	15 25 °C	15 25 °C	5 25 °C	15 25 °C	15 25 °C
Ambient condition for operation	Maximum storage life 2 years at 40 to 60 % humidity, operating temperature perma- nent up to 65 °C, up to 80 °C for 200 cycles	Maximum storage life 2 years at 40 to 60 % humidity, operating temperature perma- nent up to 65 °C, up to 80 °C for 200 cycles	Maximum storage life 2 years at 45 to 55 % humidity, operating temperature perma- nent up to 85 °C, short term -40 °C to 160 °C for 90 minutes	Maximum storage life 2 years at 40 to 60 % humidity, operating temperature perma- nent up to 65 °C, up to 80 °C for 200 cycles	Maximum storage life 2 years at 40 to 60 % humidity, operating temperature perma- nent up to 65 °C, up to 80 °C for 200 cycles
Protection class IP	IP60, in glued condi- tion, the label must be protected against humidity	IP60, in glued condi- tion, the label must be protected against humidity	IP60, in glued condi- tion, the label must be protected against humidity	IP65	IP65
Resistance to mechanical stress	Torsion and bending stress conditionally permissible	Torsion and bending stress conditionally permissible	Torsion and bending stress conditionally permissible	Torsion and bending stress conditionally permissible	Torsion and bending stress conditionally permissible

Technical specifications

RF630L

Article number	6GT2810-2AB00	6GT2810-2AB01	6GT2810-2AE81- 0AX1	6GT2810-2AB02- 0AX0	6GT2810-2AB03
Product type designation	RF630L transponder	RF630L transponder	RF630L transponder	RF630L transponder	RF630L transponder
Suitability for operation	RF600	RF600	RF600	RF600	RF600
Design, dimensions and weight					
Width	101 mm	101 mm	30 mm	27 mm	34 mm
Height	0.3 mm	0.3 mm	0.3 mm	0.3 mm	0.3 mm
Depth	152 mm	50 mm	90 mm	97 mm	54 mm
Net weight	3 g	2 g	1 g	1 g	1 g
Mounting type	one-side adhesible onto paper / card- board	one-side adhesible onto paper / card- board	one-side adhesible	one-side adhesible onto plastic / foil	one-side adhesible onto plastic / foil
Product properties, functions, components general					
Product feature					
printable	Yes	Yes	Yes	Yes	Yes
Printing process	Thermal transfer process	Thermal transfer process	Thermal transfer process	Thermal transfer process (currently only using Toshiba B-SX4T)	Thermal transfer process (currently only using Toshiba B-SX4T)

Selection and ordering data

	Article No.
SIMATIC RF630L SmartLabel	
Frequency 865 to 960 MHz (ETSI, FCC)	
 Paper, adhesive on one side, 100 mm x 150 mm (4" x 6"); Ordering quantity 1 600 units (supplied on rolls) or a multiple thereof. 	6GT2810-2AB00
 Paper, adhesive on one side, 101 mm x 50 mm (4* x 2*); Ordering quantity 1 000 units (supplied on rolls) or a multiple thereof. 	6GT2810-2AB01
 Plastic PET, adhesive on one side, 90 mm x 30 mm (3.5" x 1.18"); Ordering quantity 7 000 units (supplied on rolls) or a multiple thereof. 	6GT2810-2AE81-0AX1
 Plastic PET, adhesive on one side, 97 mm x 27 mm (3.8" x 1.1"); Ordering quantity 5 000 units (supplied on rolls) or a multiple thereof. 	6GT2810-2AB02-0AX0
• Plastic PET, adhesive on one side, 54 mm x 34 mm (2.1" x 1.3"); Ordering quantity 2 000 units (supplied on rolls) or a multiple thereof.	6GT2810-2AB03

RF640L

Overview



The SIMATIC RF640L on-metal label is designed for direct mounting on metal surfaces and under these conditions achieves a read range of up to 3.5 m.

The on-metal label is suitable for applications in industrial plant management, RF identification of tools, containers and metallic equipment.

This transponder is available in two frequency versions for 865 to 868 MHz (ETSI) and 902 to 928 MHz (FCC, CMIIT).



Technical specifications

Article number	6GT2810-2AC00	6GT2810-2AC10
Product type designation	BE640L transponder	BE640L transponder
Suitability for operation	BE600	BE600
Wireless frequencies		
Operating frequency	865 868 MHz	902 928 MHz
Electrical data		
Bange maximum	3.5 m:	3.5 m [.]
	observe system manual RF600: overrange is possible, range is reader dependent: observe	observe system manual RF600: overrange is possible, range is reader dependent: observe
	http://support.automation.siemens.com/WW/view/en/67384	964
Protocol with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6C	EPCglobal Class 1 Gen 2 / ISO 18000-6C
Transfer rate with radio transmission maximum	320 kbit/s	320 kbit/s
Product feature multitag-capable	Yes	Yes
Polarization	Linear	Linear
Product component Backup battery	No	No
Memory		
Type of memory	EEPROM	EEPROM
Storage capacity of the user memory	64 byte	64 byte
Type of memory organization	EPC memory 96/480 bits, user memory 64/16 bytes (512/128 bits), TID memory 12 bytes	EPC memory 96/480 bits, user memory 64/16 bytes (512/128 bits), TID memory 12 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	500	500
Data retention time at ambient temperature < 40 °C not less than	50 y	50 y
Property of memory	lock, unlock, kill, write protection, password protection	lock, unlock, kill, write protection, password protection
Type of transponder chip used	Alien Higgs 3	Alien Higgs 3
Mechanical data		
Material	Top side: PET	Top side: PET
Color	white	white
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm
Permitted ambient conditions		
Ambient temperature		
 during read/write access 	-20 +85 °C	-20 +85 °C
 outside the read/write area 	-25 +85 °C	-25 +85 °C
 during storage 	13 23 °C	13 23 °C
Protection class IP	IP67	IP67
Resistance to mechanical stress	Torsion and bending stress conditionally permissible	Torsion and bending stress conditionally permissible

RF640L

Article number	6GT2810-2AC00	6GT2810-2AC10
Product type designation	RF640L transponder	RF640L transponder
Suitability for operation	RF600	RF600
Design, dimensions and weight		
Width	50 mm	50 mm
Height	1.6 mm	1.6 mm
Depth	22.5 mm	22.5 mm
Net weight	4 g	4 g
Mounting type	one-side adhesible	one-side adhesible
Product properties, functions, components general		
Product feature		
• silicon-free	Yes	Yes
printable	Yes	Yes
Printing process	Thermal transfer process	Thermal transfer process

Selection and ordering data

	Article No.
SIMATIC RF640L on-metal-label	
UHF Class 1 Gen2 technology (EPC 96 480 bits; 16 64 bytes of user memory)	
Ordering quantity 500 units (supplied on rolls) or a multiple thereof.	
 Frequency 865 868 MHz (Europe) 	6GT2810-2AC00
 Frequency 902 928 MHz (USA, Canada) 	6GT2810-2AC10

SIMATIC RF600 transponders

RF680L

Overview





SIMATIC RF680L is a heat-resistant SmartLabel that is suitable for the identification of objects in production and logistics with high temperature requirements (e.g. for the identification of products in the paint shop/drying area).

The storage capacity is 96/240 bits for the Electronic Product Code (EPC) and 512 bits for user memory. Thanks to its broadband design, the SIMATIC RF680L SmartLabel can be used in numerous countries.

Technical specifications

Article number	6GT2810-2AG80
Product type designation	RF680L transponder
Suitability for operation	RF600
Wireless frequencies	
Operating frequency	860 960 MHz
Electrical data	
Range maximum	4 m; observe system manual RF600: overrange is possible, range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6C
Transfer rate with radio transmission maximum	320 kbit/s
Product feature multitag-capable	Yes
Polarization	Linear
Product component Backup battery	No
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	64 byte
Type of memory organization	EPC memory 96/240 bits, user memory 64 bytes (512 bits), TID memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	100 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	lock, unlock, kill, write protection, password protection
Type of transponder chip used	NXP G2XM

Article number	6GT2810-2AG80
Product type designation	RF680L transponder
Suitability for operation	RF600
Mechanical data	
Material	Paper
Color	beige
Mounting distance relating to metal surfaces recommended minimum	3 mm
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-25 +85 °C
 outside the read/write area 	-40 +230 °C
 during storage 	-40 +85 °C
Ambient condition for operation	Operating temperature permanent up to 85 °C, for 6 hours up to 200 °C, for 1 hour up to 220 °C, short-term up to 230 °C
Protection class IP	IP60, the label must be protected against humidity
Resistance to mechanical stress	Torsion and bending stress conditionally permissible
Design, dimensions and weight	
Width	54 mm
Height	0.3 mm
Depth	89 mm
Net weight	3 g
Mounting type	gluing, cable tie, screwing
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
printable	Yes
Printing process	Thermal transfer process

Selection and ordering data

Article No.	
SIMATIC RF680L SmartLabel	6GT2810-2AG80
Frequency 865 to 960 MHz (ETSI, FCC)	
Ordering quantity 1 000 units (supplied on rolls) or a multiple thereof.	

3

SIMATIC RF600 transponders

RF690L

Overview



The SIMATIC RF690L heat-resistant on-metal label is designed for direct mounting on metal surfaces and under these condi-tions achieves a read range of up to 5 m.

This transponder is available in two frequency versions for 865 to 868 MHz (ETSI) and 902 to 928 MHz (FCC, CMIIT).



Technical specifications		
Article number	6GT2810-2AG00	6GT2810-2AG10
Product type designation	RE690L transponder	RE690L transponder
Suitability for operation	RF600	RF600
Wireless frequencies		
Operating frequency	865 868 MHz	902 928 MHz
Electrical data		
Range maximum	5 m; observe system manual RF600: overrange is possible, range is reader dependent: observe http://support.automation.siemens.com/WW/view/en/6738	5 m; observe system manual RF600: overrange is possible, range is reader dependent: observe
Protocol with radio transmission	EPColobal Class 1 Gen 2 / ISO 18000-6C	EPCalobal Class 1 Gen 2 / ISO 18000-6C
Transfer rate with radio transmission maximum	320 kbit/s	320 kbit/s
Product feature multitag-capable	Yes	Yes
Polarization	Linear	Linear
Product component Backup battery	No	No
Memory		
Type of memory	EEPROM	EEPROM
Storage capacity of the user memory	64 byte	64 byte
Type of memory organization	EPC memory 96/480 bits, user memory 64/16 bytes (512/128 bits), TID memory 12 bytes	EPC memory 96/480 bits, user memory 64/16 bytes (512/128 bits), TID memory 12 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	500	500
Data retention time at ambient temperature < 40 °C not less than	50 у	50 у
Property of memory	lock, unlock, kill, write protection, password protection	lock, unlock, kill, write protection, password protection
Type of transponder chip used	Alien Higgs 3	Alien Higgs 3
Mechanical data		
Material	Top side: PET	Top side: PET
Color	beige / silver	beige / silver
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm
Permitted ambient conditions		
Ambient temperature		
during read/write access	-25 +85 °C	-25 +85 °C
outside the read/write area	Higher temperatures on request	Higher temperatures on request
during storage	13 23 °C	13 23 °C
Ambient condition for operation	Operating temperature permanent up to 85 °C, higher temperatures on request	Operating temperature permanent up to 85 °C, higher temperatures on request
Protection class IP	IFO/	IF0/
nesistance to mechanical stress	torsion and bending stress conditionally permissible	forsion and bending stress conditionally permissible

- 1	 1	(n)	r. 1	
	-			
		P = 1		

Article number	6GT2810-2AG00	6GT2810-2AG10
Product type designation	RF690L transponder RF690L transponder	
Suitability for operation	RF600	RF600
Design, dimensions and weight		
Width	88 mm	75 mm
Height	1.6 mm	1.6 mm
Depth	25 mm	25 mm
Net weight	5 g	5 g
Mounting type	one-side adhesible	one-side adhesible
Product properties, functions, components general		
Product feature		
• silicon-free	Yes	Yes
printable	Yes	Yes
Printing process	Thermal transfer process	Thermal transfer process

Selection and ordering data

	Article No.
SIMATIC RF690L heat-resistant on-metal-label	
UHF Class 1 Gen2 technology (EPC 96 480 bits; 16 64 bytes of user memory)	
Ordering quantity 400 units (sup- plied on rolls) or a multiple thereof.	
 Frequency 865 868 MHz (Europe) 	6GT2810-2AG00
 Frequency 902 928 MHz (USA, Canada) 	6GT2810-2AG10

SIMATIC RF600 transponders

RF610T

Overview



The SIMATIC RF610T transponder is a flexible card in ISO format that is suitable for a wide variety of applications, e.g. for identification of containers, pallets, vessels, or trolleys. SIMATIC RF610T can be attached to the most diverse materials, including plastic, wood, glass and, with a spacer, metal.

The plastic enclosure is designed for food safety and is therefore also suitable for use with food and beverages. Thanks to its broadband design, the transponder can be used in numerous countries.



6GT2810-2BB80

6GT28102BB80-0AX1

Technical specifications

Article number	6GT2810-2BB80	6GT2810-2BB80-0AX1	
Product type designation	RF610T transponder	RF610T transponder	
Suitability for operation	RF600	RF600	
Wireless frequencies			
Operating frequency	860 960 MHz	860 960 MHz	
Electrical data			
Range maximum	5 m; observe system manual RF600: overrange is possible, range is reader dependent: observe	5 m; observe system manual RF600: overrange is possible, range is reader dependent: observe	
	http://support.automation.siemens.com/WW/view/en/67384	964	
Protocol with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6C	EPCglobal Class 1 Gen 2 / ISO 18000-6C	
Transfer rate with radio transmission maximum	320 kbit/s	320 kbit/s	
Product feature multitag-capable	Yes	Yes	
Polarization	Linear	Linear	
Product component Backup battery	No	No	
Memory			
Type of memory	EEPROM	EEPROM	
Storage capacity of the user memory	64 byte	64 byte	
Type of memory organization	EPC memory 96/240 bits, user memory 64 bytes (512 bits), TID memory 8 bytes	EPC memory 96/240 bits, user memory 64 bytes (512 bits), TID memory 8 bytes	
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000	100 000 000 000 000	
Number of write cycles at ambient temperature < 40 °C maximum	100 000	100 000	
Data retention time at ambient temperature < 40 °C not less than	10 y	10 y	
Property of memory	lock, unlock, write protection, password protection	lock, unlock, write protection, password protection	
Type of transponder chip used	NXP G2XM	NXP G2XM	
-	61	10	5
---	----	-----	---
1	0	IJU	L

Article number	6GT2810-2BB80	6GT2810-2BB80-0AX1
Product type designation	RF610T transponder	RF610T transponder
Suitability for operation	RF600	RF600
Mechanical data		
Material	PVC, food-safe	PVC, food-safe
Color	white	white
Mounting distance relating to metal surfaces recommended minimum	3 mm	3 mm
Permitted ambient conditions		
Ambient temperature		
 during read/write access 	-25 +85 °C	-25 +85 °C
 outside the read/write area 	-40 +85 °C	-40 +85 °C
 during storage 	-40 +85 °C	-40 +85 °C
Protection class IP	IP67	IP67
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²	1 000 m/s ²
Vibrational acceleration	500 m/s ²	500 m/s ²
Resistance to mechanical stress	Torsion and bending stress conditionally permissible	Torsion and bending stress conditionally permissible
Design, dimensions and weight		
Width	54 mm	54 mm
Height	0.4 mm	0.4 mm
Depth	86 mm	86 mm
Net weight	3 g	3 g
Mounting type	gluing, cable tie, screwing	gluing, cable tie, screwing
Product properties, functions, components general		
Product feature		
printable	Yes	Yes
Printing process	Thermal transfer process	Thermal transfer process
Standards, specifications, approvals		
Certificate of suitability		Ex: II 3 G Ex ic IIB T6 to T4, II 3 D Ex ic IIIB T120°C, -25 °C < Ta < +85 °C
MTBF	1 712 у	1 712 y
Accessories		

Selection and ordering data

	Article No.		Articl
SIMATIC RF610T ISO card transponder		Spacer	6GT21
• Frequency 865 MHz to 960 MHz (ETSI, FCC). Ordering quantity 500 units or a multiple thereof.	6GT2810-2BB80	to metal surfaces, in combination with fixing pocket 6GT2190-0AB00.	
 Same as before but with ATEX certification Ordering quantity 1 000 units or a multiple thereof. 	6GT2810-2BB80-0AX0	Ordering quantity 50 units or a multiple thereof.	
Accessories			
Fixing pocket	6GT2190-0AB00		
For SIMATIC RF610T, for attaching to metal surfaces in combination with spacer 6GT2190-0AA00. Ordering quantity 50 units or a multiple thereof		and the second s	
ordening quantity so units of a multiple thereof.		Dimensional drawings	
		Ŭ	
		SIEMENS SMATIC RF610T 6GT2810-28880 AS:A	↑
		Ø 5.0	54
		0	~ .

86

G_FS10_XX_00390

SIMATIC RF600 transponders

RF620T

Overview





The SIMATIC RF620T container transponder is designed for industrial requirements and has a high immunity to environmental effects and detergents. It can be attached to plastic, wood or glass. The RF620T can also be mounted on metal and ESD plastic with a spacer.

The SIMATIC RF620T transponder is suitable for identification of transport containers, pallets or vessels. The plastic enclosure is food safe. Thanks to its broadband design, the transponder can be used in numerous countries.

Technical specifications

Article number	6GT2810-2HC81
Product type designation	RF620T transponder
Suitability for operation	RF600
Wireless frequencies	
Operating frequency	860 960 MHz
Electrical data	
Range maximum	8 m; observe system manual RF600: overrange is possible, range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6C
Transfer rate with radio transmission maximum	320 kbit/s
Product feature multitag-capable	Yes
Polarization	Linear
Product component Backup battery	No
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	64 byte
Type of memory organization	EPC memory 96/128 bits, user memory 64 bytes (512 bits), TID memory 4 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	100 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	lock, unlock, write protection, password protection
Type of transponder chip used	IMPINJ MONZA 4QT

Article number	6GT2810-2HC81
Product type designation	RF620T transponder
Suitability for operation	RF600
Mechanical data	
Material	PP (polypropylene)
Color	anthracite
Tightening torque of the screw for securing the equipment maximum	1.2 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-25 +85 °C
 outside the read/write area 	-40 +85 °C
 during storage 	-40 +80 °C
Protection class IP	IP67
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	500 m/s ²
Resistance to mechanical stress	Torsion and bending stress not per- missible
Design, dimensions and weight	
Width	38 mm
Height	6 mm
Depth	127 mm
Net weight	18 g
Mounting type	gluing, 2 x M5 screws, spacer (see accessories)
Product properties, functions, components general	
Product feature	
printable	Yes
Printing process	Laser inscription
Accessories	
Accessories	Spacers

RF620T

Selection and ordering data		Dimensional drawings
	Article No.	
SIMATIC RF620T container transponder	6GT2810-2HC81	
Frequency 860 MHz to 960 MHz (ETSI, FCC)		
Ordering quantity 20 units or a multiple thereof.		
Accessories		
Spacer	6GT2898-2AA00	
For SIMATIC RF620T, for mounting on metal; dimensions L x W x H (mm) 155 x 38 x 12		
Ordering quantity 20 units or a multiple thereof.		
		Ø 5
		FS10_00295

SIMATIC RF620T container transponder

SIMATIC RF600 transponders

RF622T

Overview





The SIMATIC RF622T transponder has a capacity of 4 KB FRAM, and enables the storage of up to 3 424 bytes of user data on tagged objects, as well as facilitating rapid access to them. It is therefore ideally suited to use in distributed configurations in the fields of production control, asset management and intra-logistics.

The SIMATIC RF622T offers a considerable reading range of up to 3 meters on non-metallic surfaces. It can also be fixed directly to metal surfaces using the optional spacer.

Technical specifications

Article number	6GT2810-4HC80
Product type designation	RF622T transponder
Suitability for operation	RF600
Wireless frequencies	
Operating frequency	860 960 MHz
Electrical data	
Range maximum	3 m; observe system manual RF600: overrange is possible, range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6C
Transfer rate with radio transmission maximum	320 kbit/s
Product feature multitag-capable	Yes
Polarization	Linear
Product component Backup battery	No
Memory	
Type of memory	FRAM
Storage capacity of the user memory	3 424 byte
Type of memory organization	EPC memory 496 bits, user memory 3 424 bytes, TID memory 32 bytes
Number of read cycles at ambient temperature < 40 °C maximum	10 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	10 000 000 000
Data retention time at ambient temperature < 40 °C not less than	10 y
Property of memory	lock, unlock, write protection, pass- word protection
Type of transponder chip used	Fujitsu MB97R803

Article number	6GT2810-4HC80
Product type designation	RF622T transponder
Suitability for operation	RF600
Mechanical data	
Material	PA12
Color	anthracite
Tightening torque of the screw for securing the equipment maximum	1 Nm
Mounting distance relating to metal surfaces recommended minimum	5 mm
Permitted ambient conditions	
Ambient temperature	
 during read/write access 	-20 +85 °C
 outside the read/write area 	-40 +85 °C
 during storage 	-40 +80 °C
Protection class IP	IP67
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²
Vibrational acceleration	500 m/s ²
Resistance to mechanical stress	Torsion and bending stress not permissible
Design, dimensions and weight	
Width	120 mm
Height	6.5 mm
Depth	30 mm
Net weight	4 g
Mounting type	2 screws M4, spacer (see accessories)
Product properties, functions, components general	
Product feature	
• silicon-free	Yes
printable	Yes
Printing process	Laser inscription
Accessories	
Accessories	Spacers

SIMATIC RF600 transponders



SIMATIC RF600 transponders

RF625T

Overview



CCT0010 0EE00



Technical specifications

The SIMATIC RF625T disk transponder can be recessed in metal, as well as flush-mounted on metal and on non-metallic surfaces.

Thanks to its rugged design and high IP68 degree of protection, it is ideal for use in industrial environments, even for demanding production processes.

The SIMATIC RF625T can not only be used for applications in the field of installation, production and logistics, but also for the permanent equipping of tools, machines and plants for RFID-based asset management.

This transponder is available in two frequency versions for 865 to 868 MHz (ETSI) and 902 to 928 MHz (FCC, CMIIT).

COT0010 0EE01

Article number	6GT2810-2EE00	6GT2810-2EE01
Product type designation	RF625T transponder	RF625T transponder
Suitability for operation	RF600	RF600
Wireless frequencies		
Operating frequency	865 868 MHz	902 928 MHz
Electrical data		
Range maximum	1.5 m; observe system manual RF600: overrange is possible, range is reader dependent: observe	1.5 m; observe system manual RF600: overrange is possible, range is reader dependent: observe
	http://support.automation.siemens.com/WW/view/en/67384	964
Protocol with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6C	EPCglobal Class 1 Gen 2 / ISO 18000-6C
Transfer rate with radio transmission maximum	320 kbit/s	320 kbit/s
Product feature multitag-capable	Yes	Yes
Polarization	Linear	Linear
Product component Backup battery	No	No
Memory		
Type of memory	EEPROM	EEPROM
Storage capacity of the user memory	64 byte	64 byte
Type of memory organization	EPC memory 96/128 bits, user memory 64 bytes (512 bits), TID memory 4 bytes	EPC memory 96/128 bits, user memory 64 bytes (512 bits), TID memory 4 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	100 000	100 000
Data retention time at ambient temperature < 40 °C not less than	10 y	10 y
Property of memory	lock, unlock, write protection, password protection	lock, unlock, write protection, password protection
Type of transponder chip used	IMPINJ MONZA 4QT	IMPINJ MONZA 4QT
Mechanical data		
Material	PA6.6	PA6.6
Color	black	black
Tightening torque of the screw for securing the equipment maximum	1 Nm	1 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm

	~	1.	
IF1	07	4.	1
_		_	

Article number	6GT2810-2EE00	6GT2810-2EE01
Product type designation	RF625T transponder	RF625T transponder
Suitability for operation	RF600	RF600
Permitted ambient conditions		
Ambient temperature		
 during read/write access 	-25 +85 °C	-25 +85 °C
 outside the read/write area 	-40 +125 °C	-40 +125 °C
 during storage 	-40 +125 °C	-40 +125 °C
Protection class IP	IP68 / IPx9K	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²	1 000 m/s ²
Vibrational acceleration	500 m/s ²	500 m/s ²
Design, dimensions and weight		
Height	8 mm	8 mm
Diameter	30 mm	30 mm
Mounting type	gluing, M3 screw	gluing, M3 screw
Product properties, functions, components general		
Product feature		
printable	No	No
Standards, specifications, approvals		
MTBF	1 141 y	1 141 y

Selection and ordering data

	Article No.
SIMATIC RF625T disk transponder	
Ordering quantity 20 units or a multiple thereof.	
 Frequency 865 MHz to 868 MHz (ETSI) 	6GT2810-2EE00
 Frequency 902 MHz to 928 MHz (FCC) 	6GT2810-2EE01

Dimensional drawings



SIMATIC RF625T disk transponder

SIMATIC RF600 transponders

RF630T

Overview



ISO META



6

The SIMATIC RF630T screw transponder is particularly suitable for controlling and monitoring production processes. It can be automatically screwed on to products such as motors or gearbox casings by means of robots and using the M6 grub screw.

The SIMATIC RF630T is suitable for industrial requirements. Its is rugged and highly resistant to detergents.

It can be attached to materials such as plastic or wood as well as directly onto metal.

This transponder is available in two frequency versions for 865 to 868 MHz (ETSI) and 902 to 928 MHz (FCC, CMIIT).

Article number	6GT2810-2EC00	6GT2810-2EC10
Product type designation	RF630T transponder RF630T transponder	
Suitability for operation	RF600 RF600	
Wireless frequencies		
Operating frequency	865 868 MHz	902 928 MHz
Electrical data		
Range maximum	2 m; observe system manual RF600: overrange is possible, range is reader dependent: observe	2 m; observe system manual RF600: overrange is possible, range is reader dependent: observe
	http://support.automation.siemens.com/WW/view/en/67384	964
Protocol with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6C	EPCglobal Class 1 Gen 2 / ISO 18000-6C
Transfer rate with radio transmission maximum	320 kbit/s	320 kbit/s
Product feature multitag-capable	Yes	Yes
Polarization	Linear	Linear
Product component Backup battery	No	No
Memory		
Type of memory	EEPROM	EEPROM
Storage capacity of the user memory	64 byte	64 byte
Type of memory organization	EPC memory 96/240 bits, user memory 64 bytes (512 bits), TID memory 8 bytes	EPC memory 96/240 bits, user memory 64 bytes (512 bits), TID memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	100 000	100 000
Data retention time at ambient temperature < 40 °C not less than	10 у	10 y
Property of memory	lock, unlock, write protection, password protection	lock, unlock, write protection, password protection
Type of transponder chip used	NXP G2XM	NXP G2XM
Mechanical data		
Material	PA6.6 GF / stainless steel	PA6.6 GF / stainless steel
Color	black silver	black silver
Tightening torque of the screw for securing the equipment maximum	6 Nm	6 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm

	2	9	n	
1	U	J	U	L

Article number	6GT2810-2EC00	6GT2810-2EC10
Product type designation	RF630T transponder	RF630T transponder
Suitability for operation	RF600	RF600
Permitted ambient conditions		
Ambient temperature		
 during read/write access 	-25 +85 °C	-25 +85 °C
 outside the read/write area 	-40 +125 °C	-40 +125 °C
 during storage 	-40 +125 °C	-40 +125 °C
Protection class IP	IP68 / IPx9K	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²	1 000 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Height	20 mm	20 mm
Diameter	21 mm	21 mm
Net weight	22 g	22 g
Mounting type	screwing (M6)	screwing (M6)
Product properties, functions, components general		
Product feature		
printable	No	No
Standards, specifications, approvals		
MTBF	1 712 у	1 712 у

Selection and ordering data

Selection and ordering data	a	Dimensional drawings	
	Article No.		
SIMATIC RF630T screw transponder		21	SW 19
Ordering quantity 10 units or a multiple thereof.			
 Frequency 865 to 868 MHz (ETSI) 	6GT2810-2EC00	50	
 Frequency 902 to 928 MHz (FCC) 	6GT2810-2EC10		
		1	M6 Pist

SIMATIC RF630T screw transponder

SIMATIC RF600 transponders

RF640T

Overview



The SIMATIC RF640T tool transponder can be used directly on metal, and is therefore particularly suitable for tracking tools, containers and metallic equipment (asset management).

Its rugged and yet compact design, its high degree of protection (IP68/IPx9K) and resistance to mineral oils, lubricants and cleaning agents make it the first choice in industrial environments. The European version has ATEX approval.

This transponder is available in two frequency versions for 865 to 868 MHz (ETSI) and 902 to 928 MHz (FCC, CMIIT).

Technical specifications

A		
Article number	6G12810-2DC00	6G12810-2DC10
Product type designation	RF640T transponder	RF640T transponder
Suitability for operation	RF600	RF600
Wireless frequencies		
Operating frequency	865 868 MHz	902 928 MHz
Electrical data		
Range maximum	4 m; observe system manual RF600: overrange is possible, range is reader dependent: observe	4 m; observe system manual RF600: overrange is possible, range is reader dependent: observe
	http://support.automation.siemens.com/WW/view/en/67384	964
Protocol with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6C	EPCglobal Class 1 Gen 2 / ISO 18000-6C
Transfer rate with radio transmission maximum	320 kbit/s	320 kbit/s
Product feature multitag-capable	Yes	Yes
Polarization	Linear	Linear
Product component Backup battery	No	No
Memory		
Type of memory	EEPROM	EEPROM
Storage capacity of the user memory	64 byte	64 byte
Type of memory organization	EPC memory 96/240 bits, user memory 64 bytes (512 bits), TID memory 8 bytes	EPC memory 96/240 bits, user memory 64 bytes (512 bits), TID memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	100 000	100 000
Data retention time at ambient temperature < 40 °C not less than	10 y	10 y
Property of memory	lock, unlock, write protection, password protection	lock, unlock, write protection, password protection
Type of transponder chip used	NXP G2XM	NXP G2XM

		RF640T
Article number	6GT2810-2DC00	6GT2810-2DC10
Product type designation	RF640T transponder	RF640T transponder
Suitability for operation	RF600	RF600
Mechanical data		
Material	PA12	PA12
Color	anthracite	anthracite
Tightening torque of the screw for securing the equipment maximum	1.2 Nm	1.2 Nm
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm
Permitted ambient conditions		
Ambient temperature		
 during read/write access 	-25 +85 °C	-25 +85 °C
 outside the read/write area 	-40 +125 °C	-40 +125 °C
 during storage 	-40 +125 °C	-40 +125 °C
Protection class IP	IP68 / IPx9K	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1 000 m/s ²	1 000 m/s ²
Vibrational acceleration	200 m/s ²	200 m/s ²
Design, dimensions and weight		
Height	8 mm	8 mm
Diameter	50 mm	50 mm
Net weight	13 g	13 g
Mounting type	2 x M4 screws	2 x M4 screws
Product properties, functions, components general		
Product feature		
silicon-free	Yes	Yes
printable	No	No
Standards, specifications, approvals		
Certificate of suitability	Ex: II 2 G Ex ib IIC T6 to T3, II 2 D Ex ibD 21 T140°C, -25 °C < Ta°< +85 °C	
MTBF	1 757 у	1 757 у

Selection and ordering data

	Article No.
SIMATIC RF640T tool transponder	
Ordering quantity 10 units or a multiple thereof.	
 Frequency 865 MHz to 868 MHz (ETSI) 	6GT2810-2DC00
Frequency 902 MHz to 928 MHz (FCC)	6GT2810-2DC10

Dimensional drawings



SIMATIC RF640T tool transponder

SIMATIC RF600 transponders

RF680T

Overview





The heat-resistant SIMATIC RF680T transponder has a wide range and, thanks to its high IP68/IPx9K degree of protection and its resistance to chemicals, it can even be used in harsh industrial applications, for example, in automotive production (including identification of skids in paint shops) or in the chemical industry. The transponder is silicon-free and withstands temperatures up to 220 °C. The storage capacity is 96/240 bit Electronic Product Code (EPC) plus 512-bit user memory. Thanks to its broadband design, the transponder can be used in numerous countries. The European version has ATEX approval.

Technical specifications	
Article number	6GT2810-2HG80
Product type designation	RF680T transponder
Suitability for operation	RF600
Wireless frequencies	
Operating frequency	865 928 MHz
Electrical data	
Range maximum	4 m; observe system manual RF600: overrange is possible, range is reader dependent: observe
http://support.automation.siemens.com	n/WW/view/en/67384964
Protocol with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6C
Transfer rate with radio transmission maximum	320 kbit/s
Product feature multitag-capable	Yes
Polarization	Linear
Product component Backup battery	No
Memory	
Type of memory	EEPROM
Storage capacity of the user memory	64 byte
Type of memory organization	EPC memory 96/240 bits, user memory 64 bytes (512 bits), TID memory 8 bytes
Number of read cycles at ambient temperature < 40 °C maximum	100 000 000 000 000
Number of write cycles at ambient temperature < 40 °C maximum	100 000
Data retention time at ambient temperature < 40 °C not less than	10 у
Property of memory	lock, unlock, write protection, password protection
Type of transponder chip used	NXP G2XM

Article number	6GT2810-2HG80	
Product type designation	RF680T transponder	
Suitability for operation	RF600	
Mechanical data		
Material	PPS	
Color	black	
Tightening torque of the screw for securing the equipment maximum	1 Nm	
Mounting distance relating to metal surfaces recommended minimum	0 mm	
Permitted ambient conditions		
Ambient temperature		
 during read/write access 	-25 +100 °C	
 outside the read/write area 	-40 +220 °C	
 during storage 	-40 +100 °C	
Ambient condition for operation	Operating temperature permanent up to 140 °C, for 5 000 hours or 3 000 cycles up to 200 °C, for 2 000 hours or 1 500 cycles up to 220 °C	
Protection class IP	IP68 / IPx9K	
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3	
Shock acceleration	1 000 m/s ²	
Vibrational acceleration	200 m/s ²	
Resistance to mechanical stress	Torsion and bending stress not permissible	
Design, dimensions and weight		
Width	32 mm	
Height	15 mm	
Depth	130 mm	
Net weight	50 g	
Mounting type	2 x M6 screws	
Product properties, functions, components general		
Product feature		
• silicon-free	Yes	
printable	No	
Standards, specifications, approvals		
Certificate of suitability	II 2G Ex ib IIB T6 to T2 Gb, II 2D Ex ib IIIB T135 °C Db	
MTBF	1 940 у	

SIMATIC RF600 transponders

Selection and ordering data Article No. SIMATIC RF680T high-temperature transponder Frequency 865 to 928 MHz (ETSI, FCC, CMIIT). Ordering quantity 10 units or a multiple thereof. Dimensional drawings upper dimensional

SIMATIC RF680T high-temperature transponder

Introduction

Overview

Reader	Features	Page	Reader	Features	Page
RF650R	The SIMATIC RF650R reader is a powerful UHF-RFID reader for use with as many as four external antennas. The reader is connected to the IT level via Ethernet and TCP/IP (XML protocol).	3/30	RF650M	The SIMATIC RF650M mobile handheld terminal is a powerful and compact RFID reader for applications in the field of production logistics, warehouse management, inventories and service. Transponder data can be displayed and edited using a preinstalled application. Furthermore, specific Windows applications can be developed for the device.	3/41
				The handheld forwards the data stored on the transponder to the downstream systems via either WLAN or the interfaces of the docking station (USB, Ethernet).	
RF680R	The SIMATIC RF680R reader is a powerful UHF-RFID reader for use with as many as four external antennas.	3/33			
and and a	There are two methods of integrating the reader into an automation system: Either directly via the integrated PROFINET interface or via the ASM 456 communication module on PROFIBUS.				
	The readers are connected to the IT level via Ethernet with TCP/IP and XML.				
RF685R	The SIMATIC RF685R reader is a powerful UHF RFID reader with an integral antenna and a connection for an external antenna.	3/37			
ALL	There are two methods of integrating the reader into an automation system: Either directly via the integrated PROFINET interface or via the ASM 456 communication module on PROFIBUS.				
	The readers are connected to the IT level via Ethernet with TCP/IP and XML.				

Overview



Software installations for commissioning or diagnostics are a thing of the past with the SIMATIC RF650R, RF680R and RF685R readers. The user interface can be easily called up with an Internet browser. In this way, maintenance engineers, for example, can connect remotely to a reader and carry out the relevant tasks from the office.

The orientation of the antennas is accomplished within a few minutes with the aid of the corresponding menu. The Webbased interface gives the user immediate feedback about how changing the antenna position or orientation affects the acquisition. Especially practical: The same information is also shown via a brightly lit LED row on the housing of the reader – so that the setup can also be performed in obstructed installations.

In the Diagnostics menu, all information necessary to assess the quality of the reading results during operation is displayed, e.g. the signal strength (RSSI), the acquisition frequency and the transmitting power effectively used.

Moreover, even the transponders filtered out on the basis of the "UHF for Industry" algorithms used are shown. The effect of these filter functions can thus be easily analyzed and their parameters quickly optimized.

A built-in diagnostics log records all events including read and write errors or changes made to the parameters of the reader. In this way, a "glimpse into the past" can be made to retrospectively analyze a sporadically occurring error, for example. 3

SIMATIC RF600 readers

RF650R

Overview



The high-performance SIMATIC RF650R reader has four antenna connections that can be configured as required for individual read stations, or as gates. The high radiated power of up to 2 W ERP / 4 W EIRP (dependent on antenna and cable) permits long ranges of up to 8 m in portal applications.

The integrated processing logic of the reader enables numerous functions of the higher-level software layers to be executed in the device itself. If necessary, the digital outputs for signaling functions are automatically controlled. The advantage of the SIMATIC RF650R is that its intelligence considerably reduces the cost for additional software modules (RFID middleware).

Configuration, commissioning and diagnosis is performed via an easy-to-use Web interface that can be operated with a standard Internet browser.

The reader supports commissioning, such as the orientation of the antenna(s), or the determining of the necessary radiant power by means of corresponding tools. A variety of diagnostic displays, such as the live radio signal diagram or the diagnostic logbook considerably simplifies and speeds up troubleshooting.

Data communication in the SIMATIC RF650R is executed by means of an XML protocol via TCP/IP. The digital inputs and outputs (DI/DO) are used for simple process interfacing (sensors, actuators).

All antennas of the RF600 series are supported.

Application

The stationary SIMATIC RF650R reader with its integral antenna is ideal for typical gate applications in logistics, distribution, supply chain management and asset management.

Technical specifications

The SIMATIC RF650R supports the established EPCglobal Class 1, Gen 2 standard, among others, and is offered in three versions: compliant with ETSI for Europe, FCC for USA/Canada, and CMIIT for China.

Article number	6GT2811-6AB20-0AA0	6GT2811-6AB20-1AA0	6GT2811-6AB20-2AA0
Product type designation	RF650R ETSI reader	RF650R FCC reader	RF650R CMIIT reader
Suitability for operation	RF600 transponders, for connecting via Ethernet	RF600 transponders, for connecting via Ethernet	RF600 transponders, for connecting via Ethernet
Wireless frequencies			
Operating frequency	865 868 MHz	902 928 MHz	920 925 MHz
Transmit power	3 1 000 mW	3 1 000 mW	3 1 000 mW
Effective radiant power			
• for each external antenna maximum	2 000 mW		2 000 mW
Equivalent isotropically radiated power			
• for each external antenna maximum		4 000 mW	
Electrical data			
Range maximum	8 m; Observe system manual RF600: Overreaches are possible, range is dependent on transponder type: observe	8 m; Observe system manual RF600: Overreaches are possible, range is dependent on transponder type: observe	8 m; Observe system manual RF600: Overreaches are possible, range is dependent on transponder type: observe
	http://support.automation.siemens.com	/WW/view/en/67384964	
Protocol with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6B/-6C	EPCglobal Class 1 Gen 2 / ISO 18000-6B/-6C	EPCglobal Class 1 Gen 2 / ISO 18000-6B/-6C
Transfer rate with radio transmission maximum	300 kbit/s	300 kbit/s	300 kbit/s
Product feature multitag-capable	Yes	Yes	Yes
Transmission time for user data			
 for write access per byte typical 	2 ms	2 ms	2 ms
 for read access per byte typical 	0.15 ms	0.15 ms	0.15 ms

Article number	6GT2811-6AB20-0AA0	6GT2811-6AB20-1AA0	6GT2811-6AB20-2AA0
Product type designation	RE650R ETSI reader	RE650R ECC reader	RF650R CMIIT reader
Interfaces			
Number of external antennas	4	4	4
Standard for interfaces for communication	Ethernet	Ethernet	Ethernet
Type of electrical connection			
 for external antenna(s) 	RP-TNC	RP-TNC	RP-TNC
for supply voltage	M12, 8-pin, connector	M12, 8-pin, connector	M12, 8-pin, connector
 for communications interface 	RJ45	RJ45	RJ45
 at the digital inputs/outputs 	M12 12-pin female connector	M12 12-pin female connector	M12 12-pin female connector
Number of digital inputs			4
Number of digital outputs	4	4	4
Mechanical data		·	·
Material	Aluminum Pocan	Aluminum Pocan	Aluminum Pocan
Color	silver TI Grov	silver TI Grov	silver TL Grov
Mounting distance relating to motal			
surfaces recommended minimum	0 mm	0 mm	Unin
Supply voltage, current consumption, power loss			
Supply voltage			
 at DC Rated value 	24 V	24 V	24 V
• at DC	20 30 V	20 30 V	20 30 V
Consumed current at DC at 24 V			
 typical 	0.37 A	0.37 A	0.37 A
• maximum	2 A	2 A	2 A
Permitted ambient conditions			
Ambient temperature			
 during operation 	-25 +55 °C	-25 +55 °C	-25 +55 °C
 during storage 	-40 +85 °C	-40 +85 °C	-40 +85 °C
 during transport 	-40 +85 °C	-40 +85 °C	-40 +85 °C
Ambient condition for operation	With operating temperature below	With operating temperature below	With operating temperature below
	Warming-up time at least 10 minutes	Warming-up time at least 10 minutes	Warming-up time at least 10 minutes
Protection class IP	IP30	IP30	IP30
Shock resistance	EN 60068-2-27	EN 60068-2-27	EN 60068-2-27
Shock, max, permissible	30 m/s ²	30 m/s ²	30 m/s ²
Vibration according to	EN 60068-2-6	EN 60068-2-6	EN 60068-2-6
Vibration, max, permissible	30 m/s ²	30 m/s ²	30 m/s ²
Design dimensions and weight			
Width	258 mm	258 mm	258 mm
Height	258 mm	258 mm	258 mm
Depth	80 mm	80 mm	80 mm
Not weight	2.4 kg	2.4 kg	2.4 kg
Mounting type	Vesa 100 with 4 x M4 screws, top-hat rail 35 mm, profile rail S7-300, S7-1200 or S7-1500	Vesa 100 with 4 x M4 screws, top-hat rail 35 mm, profile rail S7-300, S7-1200 or S7-1500	Vesa 100 with 4 x M4 screws, top-hat rail 35 mm, profile rail S7-300, S7-1200 or S7-1500
Cable length			
of antenna cable minimum	1 m	1 m	1 m
of antenna cable maximum	40 m	40 m	40 m
Product properties, functions,			
components general			
Display version	LED row with 6 LEDs	LED row with 6 LEDs	LED row with 6 LEDs
Product feature silicon-free	Yes	Yes	Yes
Standards, specifications, approvals			
Certificate of suitability	Wireless according to R&TTE guideline, CE, IEC 60950	Wireless according to FCC, IC (Canada), cULus	RaWireless according to CMIIT
MTBF	31 y	31 y	31 y
Accessories			
Accessories	up to 4 external antennas, set for mounting on top-hat rail or profile rail	up to 4 external antennas, set for mounting on top-hat rail or profile rail	up to 4 external antennas, set for mounting on top-hat rail or profile rail

RF650R

Selection and ordering data

	Article No.		Article No.
SIMATIC RF650R reader (ETSI)	6GT2811-6AB20-0AA0	Ethernet connection	
UHF RFID reader for frequencies from 865 to 868 MHz for connect- ing up to four external antennas, suitable for inclusion in IT systems via Ethernet/IP with TCP/IP.		 Ethernet cable RJ45 to RJ45, 10 m Ethernet cable RJ45 to RJ45, trailable, metal connector, 	6XV1870-3QN10 6XV1871-5Bxxx
SIMATIC RF650R reader (FCC)	6GT2811-6AB20-1AA0	various lengths	
UHF RFID reader for frequencies from 902 to 928 MHz for connect- ing up to four external antennas, suitable for inclusion in IT systems via Ethernet/IP with TCP/IP.		Set of protective caps To prevent contamination of unused connections, we recom- mend the use of protective caps. Contents:	6GT2898-4AA10
SIMATIC RF650R reader (CMIIT)	6GT2811-6AB20-2AA0	3 protective caps for antenna connection, one protective cap	
UHF RFID reader for frequencies from 920 to 925 MHz for connect- ing up to four external antennas, suitable for inclusion in IT systems via Ethernet/IP with TCP/I		for DI/DO connection, 2 protective caps for Ethernet connection. DIN rail mounting kit For mounting the reader on a	6GT2890-0AB00
Accessories		DIN rail (35 mm) or mounting rail	
Antennas		37-300/37-1300	
For proper functioning of the SIMATIC RF650R Reader, we recommend using the following antennas:			
• RF620A (siehe page 3/45)			
• RF640A (siehe page 3/48)		- 33	
 RF642A (siehe page 3/48) BE660A (siehe page 3/51) 			
DI/DQ cable	6GT2891-0CH50		
For the connection of digital sensors and actuators to SIMATIC RF650R. M12 connector on reader side, open stranded wires on sensor side. DI/DO cable, PUR material, black, shielded, M12, 12 x 0.14 mm ² , length 5 m		Dimensional drawings	
		┥╻╡╢╢╗╢╢╢╢╬╡╢╫╡	
 Wide-range power supply Primary side: 100 240 V AC, 120 353 V DC, secondary side: 24 V DC, 3 A, with no-load protec- tion, with continuous short-circuit protection EU connector version 	6GT2898-0AA00		
 UK connector version 	6GT2898-0AA10	Rom	
US connector version	6GT2898-0AA20		
Cable for wide-range power supply 24 V DC, PUR material, length 5 m.	6GT2891-0PH50	SIMATIC RF650R reader	0
Cable for 24 V nower supply	6GT2891-4EH50		
24 V DC, material PUR, trailable, length 5 m, open ends			
_// ! /			

RF680R

Overview



The high-performance SIMATIC RF680R reader has four antenna connections that can be configured as required for individual read stations, or as gates. The high radiated power of up to 2 W ERP / 4 W EIRP (dependent on antenna and cable) permits long ranges of up to 8 m in portal applications.

The integrated processing logic of the reader enables numerous functions of the higher-level software layers to be executed in the device itself. If necessary, the digital outputs for signaling functions are automatically controlled.

Application

The stationary SIMATIC RF680R reader is ideal for applications in production, production-level logistics, distribution, supply chain management, asset management, service processes or material flow control. The advantage of the SIMATIC RF680R is that its intelligence considerably reduces the cost for additional software modules (RFID middleware).

The configuration, commissioning and diagnosis is performed via an easy-to-use Web interface that can be operated with a standard Internet browser. Access to the user interface data is also possible via the TIA Portal.

The reader supports commissioning, such as the orientation of the antenna(s), or determining the radiant power required by means of corresponding software tools and of the extended LED display.

A variety of diagnostic displays, such as the live radio signal diagram or the diagnostic logbook considerably simplifies and speeds up troubleshooting.

Data communication in the RF680R is executed either via an XML protocol with TCP/IP or via an S7 protocol via PROFINET. The reader can be operated with PROFIBUS via the communication module ASM 456. Two Ethernet interfaces are available for data and diagnostics, one of which has PROFINET capability. The digital inputs and outputs (DI/DO) are used for simple process interfacing (sensors, actuators). The digital I/Os can be mapped directly into the IO image of a SIMATIC controller.

All antennas of the RF600 series are supported.

Note:

If the reader is used together with the ASM 456 communication module, be aware that only one reader can be connected to this communication module at a time. Two connected readers would exceed the maximum permissible power consumption.

The SIMATIC RF680R supports the established EPCglobal Class 1, Gen 2 standard and is offered in three versions: compliant with ETSI for Europe, FCC for USA/Canada, and CMIIT for China.

Technical specifications

Article number	6GT2811-6AA10-0AA0	6GT2811-6AA10-1AA0	6GT2811-6AA10-2AA0
Product type designation	RF680R ETSI reader	RF680R FCC reader	RF680R CMIIT reader
Suitability for operation	RF600 transponder, for direct connection to Ethernet/PROFINET or PROFIBUS via communication module	RF600 transponder, for direct connection to Ethernet/PROFINET or PROFIBUS via communication module	RF600 transponder, for direct connection to Ethernet/PROFINET or PROFIBUS via communication module
Wireless frequencies			
Operating frequency	865 868 MHz	902 928 MHz	920 925 MHz
Transmit power	3 2 000 mW	3 2 000 mW	3 2 000 mW
Effective radiant power			
• for each external antenna maximum	2 000 mW		2 000 mW
Equivalent isotropically radiated power			
• for each external antenna maximum		4 000 mW	

SIMATIC RF600 readers

RF680R			
Article number	6GT2811-6AA10-0AA0	6GT2811-6AA10-1AA0	6GT2811-6AA10-2AA0
Product type designation	RF680R ETSI reader	RF680R FCC reader	RF680R CMIIT reader
Electrical data			
Range maximum	8 m; Observe system manual RF600: Over- reaches are possible, range is depen- dent on transponder type: observe	8 m; Observe system manual RF600: Over- reaches are possible, range is depen- dent on transponder type: observe	8 m; Observe system manual RF600: Over- reaches are possible, range is depen- dent on transponder type: observe
	http://support.automation.siemens.con	n/WW/view/en/67384964	
Protocol with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6B/-6C	EPCglobal Class 1 Gen 2 / ISO 18000-6B/-6C	EPCglobal Class 1 Gen 2 / ISO 18000-6B/-6C
Transfer rate with radio transmission maximum	300 kbit/s	300 kbit/s	300 kbit/s
Product feature multitag-capable	Yes	Yes	Yes
Transmission time for user data			
 for write access per byte typical 	2 ms	2 ms	2 ms
 for read access per byte typical 	0.15 ms	0.15 ms	0.15 ms
Interfaces			
Number of external antennas	4	4	4
Standard for interfaces for communication	Ethernet/PROFINET, RS422	Ethernet/PROFINET, RS422	Ethernet/PROFINET, RS422
Type of electrical connection			
 for external antenna(s) 	RP-TNC	RP-TNC	RP-TNC
 for supply voltage 	M12, 8-pin, connector	M12, 8-pin, connector	M12, 8-pin, connector
 for communications interface 	2 x M12 4-pin D-coded, M12 8-pin (RS422)	2 x M12 4-pin D-coded, M12 8-pin (RS422)	2 x M12 4-pin D-coded, M12 8-pin (RS422)
 at the digital inputs/outputs 	M12, 12-pin, female connector	M12, 12-pin, female connector	M12, 12-pin, female connector
Number of digital inputs	4	4	4
Number of digital outputs	4	4	4
Mechanical data			
Material	Aluminum, Pocan	Aluminum, Pocan	Aluminum, Pocan
Color	silver, TI-Grey	silver, TI-Grey	silver, TI-Grey
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm	0 mm
Supply voltage, current consumption, power loss			
Supply voltage			
 at DC Rated value 	24 V	24 V	24 V
• at DC	20 30 V	20 30 V	20 30 V
Consumed current at DC at 24 V			
 typical 	0.38 A	0.38 A	0.38 A
• maximum	2 A	2 A	2 A
Permitted ambient conditions			
Ambient temperature			
 during operation 	-25 +55 °C	-25 +55 °C	-25 +55 °C
 during storage 	-40 +85 °C	-40 +85 °C	-40 +85 °C
 during transport 	-40 +85 °C	-40 +85 °C	-40 +85 °C
Ambient condition for operation	With operating temperature below -20 °C: Warming-up time at least 10 minutes	With operating temperature below -20 °C: Warming-up time at least 10 minutes	With operating temperature below -20 °C: Warming-up time at least 10 minutes
Protection class IP	IP65	IP65	IP65
Shock resistance	EN 60068-2-27	EN 60068-2-27	EN 60068-2-27
Shock, max. permissible	30 m/s ²	30 m/s ²	30 m/s ²
Vibration according to	EN 60068-2-6	EN 60068-2-6	EN 60068-2-6
Vibration, max. permissible	30 m/s ²	30 m/s ²	30 m/s ²

Article number	6GT2811-6AA10-0AA0	6GT2811-6AA10-1AA0	6GT2811-6AA10-2AA0
Product type designation	RF680R ETSI reader	RF680R FCC reader	RF680R CMIIT reader
Design, dimensions and weight			
Width	258 mm	258 mm	258 mm
Height	258 mm	258 mm	258 mm
Depth	80 mm	80 mm	80 mm
Net weight	2.4 kg	2.4 kg	2.4 kg
Mounting type	Vesa 100 with 4 x M4 screws, top-hat rail 35 mm, profile rail S7-300, S7-1200 or S7-1500	Vesa 100 with 4 x M4 screws, top-hat rail 35 mm, profile rail S7-300, S7-1200 or S7-1500	Vesa 100 with 4 x M4 screws, top-hat rail 35 mm, profile rail S7-300, S7-1200 or S7-1500
Cable length			
 of antenna cable minimum 	1 m	1 m	1 m
 of antenna cable maximum 	40 m	40 m	40 m
Product properties, functions, components general			
Display version	two LED rows with 8 and 9 LEDs	two LED rows with 8 and 9 LEDs	two LED rows with 8 and 9 LEDs
Product feature silicon-free	Yes	Yes	Yes
Standards, specifications, approvals			
Certificate of suitability	Wireless according to R&TTE guideline, CE, IEC 60950	Wireless according to FCC, IC (Canada), cULus	RaWireless according to CMIIT
MTBF	28 у	28 y	28 у
Accessories			
Accessories	up to 4 external antennas, set for mounting on top-hat rail or profile rail	up to 4 external antennas, set for mounting on top-hat rail or profile rail	up to 4 external antennas, set for mounting on top-hat rail or profile rail

RF680R

Selection and ordering data

SIMATC FF800R neader (C19) WHE FR01 reader to requences for where a net allocations and a function where a near a net allocations SIMATC FF800R neader (CNIIT) SIMATC FF800R neader (Article No.		Article No.
UHF BRUTY CREATE SUTISTI-STHED UHF AREA Connecting up to the content of the	SIMATIC RF680R reader (ETSI)	6GT2811-6AA10-0AA0	Ethernet connection	
SIMATC REFSOR reader (FCC) 6572811-6AA10-1AA0 UPF PID basis Photo in requestions in the production of production of the production	UHF RFID reader for frequencies from 865 to 868 MHz for connecting up to four external antennas, suitable for inclusion in IT systems and automation systems via Ethernet with TCP/IP and XML protocol or PROFINET.		• Ethernet cable M12 / RJ45, 5 m, RJ45 plug, obliquely angled, trailable	6XV1871-5TH50
UHF EFID neader for frequencies from optimized in the source of the contensing up to the contension up t	SIMATIC RF680R reader (FCC)	6GT2811-6AA10-1AA0		
SIMATIC RF600 reader (CMIT) 6372811-6AA10-2AA0 VEH FIP: Drade for the requestions from 320 to 926 MHz for connection suitable for inclusion in T and automation systems with a protective cap to insure the IPRS address and the IPRO Automatic Systems with a protective cap to insure the IPRS address and the IPRO Automatic Systems with a protective cap to insure the IPRS address and the IPRO Automatic Systems with a protective cap to insure the IPRS address and the IPRO Automatic Systems with a protective cap to insure the IPRS address and the IPRO Automatic Systems with a protective cap to insure the IPRS address and the IPRO Automatic Systems with a protective cap to insure the IPRS address and the IPRO Automatic Systems with a protective cap to insure the IPRS address and the IPRO Automatic Systems with a protective cap to insure the IPRS address and the IPRO Automatic Systems with a protective cap to insure the IPRS address and the IPRO Automatic Systems with a protective cap to insure the IPRS address and the IPRO Automatic Systems with a protective cap to insure the IPRS address and the IPRO Automatic Systems with a protective cap to insure the IPRS address and the IPRO Automatic Systems with a connection of digital sensors and actuators to IRS and CPRE0SO Systems and actuators to IRS and CPRE0SO Systems and the IPRO Automatic Systems with connector version CALE Crit V DC, PUR material, length 5 m. GT2889-0AA00 SGT2889-0AA20 SGT2899-0AB20 SGT2899-0AB20 SGT2899-0AB20 SGT2899-0AB20 SGT2899-0AB20 SGT2899-0AB20 SGT2899-0AB20 SGT2899-0AB20 SGT2899-0AB20 SGT2899-0AB20 SGT2899-0AB20 SGT2899-0AB20 SGT2899-0AB20 SGT2899-0AB20 SGT2899-0AB20 SGT2899-0AB20	UHF RFID reader for frequencies from 902 to 928 MHz for connecting up to four external antennas, suitable for inclusion in IT systems and automation systems via Ethernet with TCP/IP and XML protocol or PROFINET.		• Ethernet cable M12 / M12, 5 m, trailable.	6XV1870-8AH50
UHF EIRED reader for frequencies from SQN 0925.MHZ for connecting up to four external antennas, subble for up encoded or PROFINET. 6072899-4AA10 Accessories	SIMATIC RF680R reader (CMIIT)	6GT2811-6AA10-2AA0		
Accessories Mining Dickster The indo Antennas For proper functioning of the SIMATIC RF680R (see page 346) For indox indix indindinal indix indix indix indindix indix indix	UHF RFID reader for frequencies from 920 to 925 MHz for connecting up to four external antennas, suitable for inclusion in IT and automation systems via Ethernet with TCP/IP and XML protocol or PROFINET.		Set of protective caps Unused connections must be fitted	6GT2898-4AA10
Antennas Contents: For proper functioning of the SUMATIC RF600R fleader, we recommend using the following antennas: Sprotective caps for antenna connection, one protective caps for DIVDO connection, 2 protective caps for BHB/PAIA (See page 3/46) GT2890-0AB00 • RF6420A (see page 3/46) • RF6420A (see page 3/46) GT2891-0CH50 • RF6420A (see page 3/46) • GT2891-0CH50 GT2890-0AB00 • DIV calia GT2891-0CH50 GT2890-0AB00 • Protective caps for antenna connection of digital sensors and actuators to SIMATIC RF60R. Mil2 connection or neader side, on reader side, diff. GT2890-0AB00 • DIVO cable GT2891-0CH50 GT2891-0CH50 • Wide-range power supply Friedbalk (See page 3/46) GT2899-0AA00 • SUM-Caling to marker side: GT2899-0AA00 GT2899-0AA00 • SUM-Cange power supply GT2899-0AA00 GT2899-0AA00 • Wide-range power supply GT2899-0AA00 GT2899-0AA00 • GT2899-0AA10 GT2899-0AA10 GT2899-0AA00 • SU connector version GT2899-0AA20 GT2899-0A20 • Sub connector version GT2899-0A20 GT2899-0A20 • Sub connector version GT2899-0A20 GT2899-0A20 • Sub connector version GT2899-0A20 <	Accessories		safety class.	
 I-RF20A (see page 3/45) I-RF20A (see page 3/45) I-RF20A (see page 3/48) I-RE20A (see page 3/48) <l< td=""><td>Antennas For proper functioning of the SIMATIC RF680R Reader, we recommend using the following antennas:</td><td></td><td>Contents: 3 protective caps for antenna connec- tion, one protective cap for DI/DO connection, 2 protective caps for Ethernet connection.</td><td></td></l<>	Antennas For proper functioning of the SIMATIC RF680R Reader, we recommend using the following antennas:		Contents: 3 protective caps for antenna connec- tion, one protective cap for DI/DO connection, 2 protective caps for Ethernet connection.	
 Include (see page 3/46) IPF62A (see page	• RF620A (see page 3/45)		DIN rail mounting kit	6GT2890-0AB00
DIN rail (35 mp) or mounting rail S7-300/S7-1500 DIN rail (35 mp) or mounting rail DIN rail (35 mp) or mounting	 RF640A (see page 3/48) BE642A (see page 3/48) 		For mounting the reader on a	
DVDO cable 6GT2891-0CH50 For the connection of digital sensors and actuators to SIMATI C RF600. 6GT2891-0CH50 M12 connector on reader side. open stranded wires on sensors side. Di/DO cable. PUR material, black, shielded, M12, 12 × 0.14 mm², length 5 m Wide-range power supply Primary side: 100 240 V AC, 120 353 V DC, secondary side: 6GT2898-0AA00 Vide-range power supply GGT2898-0AA00 Vilk connector version 6GT2898-0AA00 UK connector version 6GT2898-0AA00 UK connector version 6GT2898-0AA00 UK connector version GGT2898-0AA00 UK connector version 6GT2898-0AA00 UK connector version GGT2898-0AA00 VUK connector version GGT2898-0AA00 UK connector version GGT2898-0AA00 VUK connector version GGT2898-0AA20 GGT2898-0AA20 GGT2891-0PH50 ZA V DC, A public height 5 m. GGT2891-4EH50 GGT2891-4EH50 GGT2891-4EH50	• RF660A (see page 3/51)		DIN rail (35 mm) or mounting rail S7-300/S7-1500	
For the connection of digital sensors and actuators of SMATIC PRESOR Image: Connector on reader side. Option stranded wires on sensor side. DI/DO cable. PUR material, black, shielded, M12. 12 x 0.14 mm, length 5 m Image: Connector on reader side. Connector version Wide-range power supply GT2898-0AA00 Primary side: 100 240 V AC, 120 353 V DC, secondary side. Connector version GT2898-0AA00 • Uk connector version GT2898-0AA00 • Uk connector version GT2898-0AA10 • Us connector version GT2898-0AA20 • Cable for 24 V power supply GT2891-0PH50 • U DC, naterial PUR, traitable, length 5 m. GT2891-0PH50 • Output: The reader supply GT2891-4EH50 • Output: The reader supply GT2891-4EH50 • Output: The reader supply GT2891-4EH50	DI/DO cable	6GT2891-0CH50		
Wide-range power supply Dimensional drawings Primary side: 100 240 V AC, 120 353 V DC, secondary side: 24 V DC, 3 A, with no-load protection, with continuous short-circuit protection 6GT2898-0AA00 • EU connector version • GGT2898-0AA10 • US connector version • GGT2898-0AA20 • GGT2898-0AA20 • GGT2898-0AA20 • US connector version • GGT2898-0AA20 • GGT2898-0AA20 • GGT2898-0AA20 • Cable for wide-range power supply • GGT2891-0PH50 24 V DC, PUR material, length 5 m. • GGT2891-4EH50 • Zable for 24 V power supply • GGT2891-4EH50 • UVC, material PUR, trailable, length 5 m, open ends • GGT2891-4EH50 • Output • GGT2891-4EH50	For the connection of digital sensors and actuators to SIMATIC RF680R. M12 connector on reader side, open stranded wires on sensor side. DI/DO cable, PUR material, black, shielded, M12, 12 x 0.14 mm ² , length 5 m			
Wide-range power supply Primary side: 100 240 V AC, 120 353 V DC, secondary side: 24 V DC, 3A, with no-load protection, with continuous short-circuit protection • EU connector version • GGT2898-0AA00 • US connector version • GGT2898-0AA20 Cable for wide-range power supply 24 V DC, PUR material, length 5 m. • Cable for 24 V power supply 24 V DC, material PUR, trailable, length 5 m, open ends • GGT2891-4EH50	No.		Dimensional drawings	
Primary side: 100 240 V AC, 120 353 V DC, secondary side: 24 V DC, 3 A, with no-load protection • EU connector version 6GT2898-0AA00 • GT2898-0AA20 • GT2898-0AA20 • GT2898-0AA20 • GT2898-0AA20 • GT2891-0PH50 • GT2891-0PH50 • GT2891-4EH50 • GT2891-4EH5	Wide-range power supply		-	
 EU connector version GGT2898-0AA00 UK connector version GGT2898-0AA10 US connector version GGT2898-0AA20 GGT2891-0PH50 GGT2891-0PH50 GGT2891-0PH50 GGT2891-4EH50 GGT2891-4EH50 GGT2891-4EH50 GGT2891-4EH50 	Primary side: 100 240 V AC, 120 353 V DC, secondary side: 24 V DC, 3 A, with no-load protection, with continuous short-circuit protection			
 UK connector version US connector version GGT2898-0AA20 GGT2898-0AA20 GGT2891-0PH50 GGT2891-0PH50 GGT2891-4EH50 GGT2891-4EH50 	EU connector version	6GT2898-0AA00	60000	
• US connector version 6GT2898-0AA20 Cable for wide-range power supply 6GT2891-0PH50 24 V DC, PUR material, length 5 m. 6GT2891-0PH50 Cable for 24 V power supply 6GT2891-4EH50 24 V DC, material PUR, trailable, length 5 m, open ends 6GT2891-4EH50	UK connector version	6GT2898-0AA10		03
Cable for wide-range power supply 6GT2891-0PH50 24 V DC, PUR material, length 5 m. 6GT2891-0PH50 Cable for 24 V power supply 6GT2891-4EH50 24 V DC, material PUR, trailable, length 5 m, open ends 6GT2891-4EH50 Image: State of the stat	US connector version	6GT2898-0AA20		
24 V DC, PUR material, length 5 m. Cable for 24 V power supply 24 V DC, material PUR, trailable, length 5 m, open ends Cable for 24 V power supply 24 V DC, material PUR, trailable, length 5 m, open ends Cable for 24 V power supply 258 Cable for 24 V power supply 24 V DC, material PUR, trailable, length 5 m, open ends Cable for 24 V power supply 258 Cable for 24 V power supply 24 V DC, material PUR, trailable, length 5 m, open ends Cable for 24 V power supply 258 Cable for 24 V power supply 24 V DC, material PUR, trailable, Length 5 m, open ends Cable for 24 V power supply 258 Cable for 24 V power supply 268 Cable for 24 V power supply	Cable for wide-range power supply	6GT2891-0PH50		
Cable for 24 V power supply 6GT2891-4EH50 24 V DC, material PUR, trailable, length 5 m, open ends 6GT2891-4EH50	24 V DC, PUR material, length 5 m.			
Cable for 24 V power supply 6GT2891-4EH50 24 V DC, material PUR, trailable, length 5 m, open ends 6GT2891-4EH50	A second s		●╡╢║┇║╓╫╢╏╬	
Cable for 24 V power supply 6GT2891-4EH50 24 V DC, material PUR, trailable, length 5 m, open ends 6GT2891-4EH50	All and the second s			
24 V DC, material PUR, trailable, length 5 m, open ends	Cable for 24 V nower supply	6GT2801-//EH50		258
length 5 m, open ends	24 V DC material PUB trailable	0012031-421130	205	0105
	length 5 m, open ends		Bassar	Theorem X

RF<u>685R</u>

Overview



The high-performance SIMATIC RF685R reader has a built-in adaptive antenna and a connection for an external antenna. This enables single reading stations with one or two antennas or two logical reading stations to be implemented for reading on conveyor systems. The high radiated power of up to 2 W ERP / 4 W EIRP (dependent on antenna and cable) permits long ranges. The high degree of protection (IP65) of the overall system enables problem-free use, even under the most difficult environmental conditions.

One special feature of the RF685R is the integrated adaptive antenna. Thanks to their variable polarization, they can achieve high reading rates, even in areas with poor radio reception. In addition, project planning and spare parts inventory management are considerably simplified. For individual reading points along a production line, the RF685R is the ideal choice of device.

Application

The SIMATIC RF685R stationary UHF reader is ideally suited for applications along a production line or for reading points that can be implemented with two antennas at maximum. The integrated processing logic of the reader enables numerous functions of the higher-level software layers to be executed in the device itself. If necessary, the digital outputs for signaling functions are automatically controlled. The advantage of the SIMATIC RF685R is that its intelligence considerably reduces the cost for additional software modules (RFID middleware). Configuration, commissioning and diagnosis is performed via an easy-to-use Web interface that can be operated with a standard Internet browser. Access to the user interface data is also possible via the TIA Portal. The reader supports commissioning, such as the orientation of the antenna(s), or determining the radiant power required by means of corresponding software tools and the extended LED display.

A variety of diagnostic displays, such as the live radio signal diagram or the diagnostic logbook considerably simplifies and speeds up troubleshooting.

Data communication in the RF685R is executed either via an XML protocol with TCP/IP or via an S7 protocol via Profinet. Two Ethernet interfaces are available for data and diagnostics, of which one has Profinet capability.

The digital inputs and outputs (DI/DO) are used for simple process interfacing (sensors, actuators). The digital I/Os can be mapped directly into the IO image of a SIMATIC controller.

All antennas of the RF600 series are supported.

Note:

If the reader is used together with the ASM 456 communication module, be aware that only one reader can be connected to this communication module at a time. Two connected readers would exceed the maximum permissible power consumption.

The SIMATIC RF685R supports the established EPCglobal Class 1, Gen 2 standard and is offered in three versions: compliant with ETSI for Europe, compliant with FCC for USA/Canada, and compliant with CMIIT for China.

RF685R

Technical specifications

Article number	6GT2811-6CA10-0AA0	6GT2811-6CA10-1AA0	6GT2811-6CA10-2AA0
Product type designation	RF685R ETSI reader RF685R FCC reader RF		RF685R CMIIT reader
Suitability for operation	RF600 transponder, for direct connection to Ethernet/PROFINET or PROFIBUS via communication module	RF600 transponder, for direct connection to Ethernet/PROFINET or PROFIBUS via communication module	RF600 transponder, for direct connection to Ethernet/PROFINET or PROFIBUS via communication module
Wireless frequencies			
Operating frequency	865 868 MHz	902 928 MHz	920 925 MHz
Transmit power	3 2 000 mW	3 2 000 mW	3 2 000 mW
Effective radiant power			
 for each external antenna maximum 	2 000 mW		2 000 mW
• minimum	10 mW		10 mW
• maximum	2 000 mW		2 000 mW
Equivalent isotropically radiated power		1000 W	
tor each external antenna maximum		4 000 mW	
• minimum		10 mW	
• maximum		4 000 mW	
Electrical data	0	0	0
Range maximum	o m; Observe system manual RF600: Overreaches are possible, range is dependent on transponder type: observe	o m; Observe system manual RF600: Overreaches are possible, range is dependent on transponder type: observe	o m; Observe system manual RF600: Overreaches are possible, range is dependent on transponder type: observe
	http://support.automation.siemens.com	///////ww/en/67384964	
	ISO 18000-6B/-6C	ISO 18000-6B/-6C	ISO 18000-6B/-6C
Transfer rate with radio transmission maximum	300 kbit/s	300 kbit/s	300 kbit/s
Product feature multitag-capable	Yes	Yes	Yes
Polarization	linear, circular, auto	linear, circular, auto	linear, circular, auto
Transmission time for user data			
for write access per byte typical	2 ms	2 ms	2 ms
for read access per byte typical	0.15 ms	0.15 ms	0.15 ms
Interfaces	4	4	
Number of external antennas			
communication	Ethernet/PROFINE I, R5422	Ethernet/PROFINE I, R5422	Ethernet/PROFINE I, R5422
Type of electrical connection		DD TNC	
• for external antenna(s)	RP-INC	RP-INC	KP-INC
for supply voltage	MI2, 8-pin, connector	MI2, 8-pin, connector	MI2, 8-pin, connector
• for communications intenace	M12 8-pin (RS422)	M12 8-pin (RS422)	M12 8-pin (RS422)
at the digital inputs/outputs	M12, 12-pin, female connector	M12, 12-pin, female connector	M12, 12-pin, female connector
Number of digital inputs	4	4	4
Number of digital outputs	4	4	4
Material	Aluminum Pocon	Aluminum Pocon	Aluminum Pocon
Color	silver TL-Grev	silver TLGrev	silver TLGrev
Mounting distance relating to metal surfaces recommended minimum	0 mm	0 mm	0 mm
Supply voltage, current consumption, power loss			
Supply voltage			
at DC Rated value	24 V	24 V	24 V
• at DC	20 30 V	20 30 V	20 30 V
Consumed current at DC at 24 V			
typical	0.38 A	0.38 A	0.38 A
• maximum	2 A	2 A	2 A

R	Ξ	68	5	R

Article number	6GT2811-6CA10-0AA0	6GT2811-6CA10-1AA0	6GT2811-6CA10-2AA0
Product type designation	RF685R ETSI reader	RF685R FCC reader	RF685R CMIIT reader
Permitted ambient conditions			
Ambient temperature			
 during operation 	-25 +55 °C	-25 +55 °C	-25 +55 °C
 during storage 	-40 +85 °C	-40 +85 °C	-40 +85 °C
 during transport 	-40 +85 °C	-40 +85 °C	-40 +85 °C
Ambient condition for operation	With operating temperature below -20 °C: Warming-up time at least 10 minutes	With operating temperature below -20 °C: Warming-up time at least 10 minutes	With operating temperature below -20 °C: Warming-up time at least 10 minutes
Protection class IP	IP65	IP65	IP65
Shock resistance	EN 60068-2-27	EN 60068-2-27	EN 60068-2-27
Shock, max. permissible	30 m/s ²	30 m/s ²	30 m/s ²
Vibration according to	EN 60068-2-6	EN 60068-2-6	EN 60068-2-6
Vibration, max. permissible	30 m/s ²	30 m/s ²	30 m/s ²
Design, dimensions and weight			
Width	258 mm	258 mm	258 mm
Height	258 mm	258 mm	258 mm
Depth	80 mm	80 mm	80 mm
Net weight	2.47 kg	2.47 kg	2.47 kg
Mounting type	Vesa 100 with 4 x M4 screws, top-hat rail 35 mm, profile rail S7-300, S7-1200 or S7-1500	Vesa 100 with 4 x M4 screws, top-hat rail 35 mm, profile rail S7-300, S7-1200 or S7-1500	Vesa 100 with 4 x M4 screws, top-hat rail 35 mm, profile rail S7-300, S7-1200 or S7-1500
Cable length			
 of antenna cable minimum 	1 m	1 m	1 m
 of antenna cable maximum 	40 m	40 m	40 m
Product properties, functions, components general			
Display version	two LED rows with 8 and 9 LEDs	two LED rows with 8 and 9 LEDs	two LED rows with 8 and 9 LEDs
Product feature silicon-free	Yes	Yes	Yes
Standards, specifications, approvals			
Certificate of suitability	Wireless according to R&TTE guideline, CE, IEC 60950	Wireless according to FCC, IC (Canada), cULus	Wireless according to CMIIT
MTBF	29 у	29 у	29 у
Accessories			
Accessories	one external antenna, set for mounting on top-hat rail or profile rail	one external antenna, set for mounting on top-hat rail or profile rail	one external antenna, set for mounting on top-hat rail or profile rail

RF685R

Selection and ordering data

	Article No	·	Article No.
		Ethomat a sum a stirm	Article No.
SIMATIC RF685R reader (ETSI) UHF RFID reader for frequencies from 865 to 868 MHz with integrated antenna. Connection for one external antenna is provided. Suitable for inclu- sion in IT and automation systems via Ethernet with TCP/IP and XML protocol or PROFINET.	6GT2811-6CA10-0AA0	Ethernet connection • Ethernet cable M12 / RJ45, 5 m, RJ45 plug, obliquely angled, trailable	6XV1871-5TH50
SIMATIC RF685R reader (FCC)	6GT2811-6CA10-1AA0		
UHF RFID reader for frequencies from 902 to 928 MHz with integrated antenna. Connection for one external antenna is provided. Suitable for inclu- sion in IT and automation systems via Ethernet with TCP/IP and XML protocol or PROFINET.		• Ethernet cable M12 / M12, 5 m, trailable	6XV1870-8AH50
SIMATIC RF685R reader (CMIIT)	6GT2811-6CA10-2AA0	E. Market	
UHF RFID reader for frequencies from 920 to 925 MHz with integrated antenna. Connection for one external antenna is provided. Suitable for inclu- sion in IT and automation systems via Ethernet with TCP/IP and XML protocol or PROFINET. Accessories Antennas		Set of protective caps Unused connections must be fitted with a protective cap to ensure the IP65 safety class. Contents: 3 protective caps for antenna connec- tion, one protective cap for DI/DO connection, 2 protective caps for	6GT2898-4AA10
For proper functioning of the SIMATIC		Ethernet connection.	
the following antennas:		DIN rail mounting kit	6GT2890-0AB00
• RF620A (see page 3/45)		For mounting the reader on a DIN rail (35 mm) or mounting rail	
• RF640A (see page 3/48)		S7-300/S7-1500	
• RF642A (see page 3/48)		-	
• RF660A (see page 3/51)		598	
DI/DO cable	6GT2891-0CH50		
For the connection of digital sensors and actuators to SIMATIC RF685R. M12 connector on reader side, open stranded wires on sensor side. DI/DO cable, PUR material, black, shielded, M12, 12 x 0.14 mm ² , length 5 m			
		Dimensional drawings	
See.			
Wide-range power supply			
Primary side: 100 240 V AC, 120 353 V DC, secondary side: 24 V DC, 3 A, with no-load protection, with continuous short-circuit protection			
EU connector version	6GT2898-0AA00		
UK connector version	6GT2898-0AA10	┥┥┫╎╎╎╎╎╎╎╎	
 US connector version 	6GT2898-0AA20		528
Cable for wide-range power supply	6GT2891-0PH50		
24 V DC, PUR material, length 5 m.			
		205	
Of the second se			X .
Cable for 24 V power supply	6GT2891-4EH50		
24 V DC, material PUR, trailable, length 5 m, open ends			o'
		SIMATIC RF685R reader	
5			

RF650M mobile handheld terminal

<section-header>

2.5 m Multitag

SIMATIC RF650M is a powerful and compact mobile RFID reader for applications in the field of production logistics, warehouse management, inventories and service. The device is also an important tool for the commissioning and testing of RFID systems. Thanks to the high transmit power, the RFID transponders can also be reliably detected at large distances.

Design

The SIMATIC RF650M handheld reader features a color touch display with a resolution of 240 x 320 pixels, rugged keypad and a large trigger button. This ensures reliable and user-friendly operation. To save space, users can fold down the RFID antenna.

The dimensions of just $147 \times 60 \times 39$ mm mean that the device can easily be carried in a pocket. Its low weight of only 235 g including rechargeable battery enables the reader to be used for long periods without fatigue.

Function

The supplied and pre-installed RF600 software provides service and test functions for reading and writing the RF600 transponders and SmartLabels (compliant with ISO 18000-6C). Data that has been read can be saved in files. To locate objects that have been equipped with a transponder, the software offers a simple localization and search function.

Based on the operating system and communication standards (WIN CE), the device ensures easy integration in existing or planned IT networks or in the process infrastructure. For this purpose, various optional development tools for the PC (Software Development Kit) can be obtained directly from Nordic ID.

The read data can be forwarded to the IT infrastructure via the integrated WLAN or via USB or Ethernet port of the docking station.

Integration



Mobile RFID data acquisition system connected via SCALANCE components

RF650M mobile handheld terminal

Technical specifications

Article number	6GT2813-0CA00	6GT2813-0CA10
Product type designation	RF650M ETSI mobile hand-held terminal	RF650M FCC mobile hand-held terminal
Suitability for operation	RF600 transponder	RF600 transponder
Range	2 500 mm, is dependent on transponder type	2 500 mm, is dependent on transponder type
Wireless frequencies		
Operating frequency	865.6 867.6 MHz	902 928 MHz
Effective radiant power	500 mW	
Equivalent isotropically radiated		820 mW
power		
Electrical data		
Protocol with radio transmission	EPCglobal Class 1 Gen 2 / ISO 18000-6C	EPCglobal Class 1 Gen 2 / ISO 18000-6C
Product feature multitag-capable	Yes	Yes
Polarization	Linear horizontal, vertical, automatic	Linear horizontal, vertical, automatic
Supply voltage, current consumption, power loss		
Type of current supply	Battery operation or mains operation	Battery operation or mains operation
Type of battery	Li-Polymer accumulator, replaceable	Li-Polymer accumulator, replaceable
Battery capacity	2.26 Ah	2.26 Ah
Operating period with standard battery typical	9 h	9 h
Permitted ambient conditions		
Ambient temperature		
 during operation 	-20 +55 °C	-20 +55 °C
 during storage 	-20 +60 °C	-20 +60 °C
Relative humidity at 25 °C without	95 %	95 %
condensation during operation		
Height of foll movimum	1.5 m	1.5 m
Protection class IP	1224	1204
Width	60 mm	60 mm
Height	147 mm	147 mm
Depth	20 mm	20 mm
Netweight	0.24 kg	0.24 kg
Product properties functions	0.24 kg	0.24 kg
components general		
Design of the display	QVGA color touch screen 2.2 inch, 240 x 320 pixels	QVGA color touch screen 2.2 inch, 240 x 320 pixels
Operator element version	Alphanumeric	Alphanumeric
Design of acoustic signaling element	Speakers	Speakers
Design of the interface	WLAN, USB and Ethernet via charging station	WLAN, USB and Ethernet via charging station
Storage capacity		
• of the RAM	256 Mibyte	256 Mibyte
 of the data and program memory 	288 Mibyte	288 Mibyte
• of the data memory can be used	256 Mibyte	256 Mibyte
Product functions management, configuration		
Operating system pre-installed	Windows Embedded CE 6.0	Windows Embedded CE 6.0
Product function of the software	Record, process, search of ISO 18000-6C transponder	Record, process, search of ISO 18000-6C transponder
Type of programming	Programming with MS Visual Studio 2008 API for	Programming with MS Visual Studio 2008 API for
Standarda specifications	several programming languages available	several programming languages available
approvals		
Certificate of suitability	EMC: EN 55022, EN 301 489, safety: EN 60950, RF: EN 302 208	EMC: EN 55022, EN 301 489, safety: EN 60950, RF: EN 302 208, FCC Part 15
MTBF	43 y	43 y
Accessories		
Accessories	Charging/docking station with USB- and Ethernet interface, changeable accumulator Li-Po 2260 mAh / 3.7 V, also included: charging device 100-240 V	Charging/docking station with USB- and Ethernet interface, changeable accumulator Li-Po 2260 mAh / 3.7 V, also included: charging device 100-240 V $$

RFID systems for the UHF range SIMATIC RF600 readers

RF650M mobile handheld terminal

Selection and ordering data		Dimensional drawings
	Article No.	-
SIMATIC RF650M (ETSI) mobile handheld terminal	6GT2813-0CA00	
Basic unit, suitable for transpon- ders conforming to EPCglobal Class 1 Gen 2 / ISO 18000-6C, incl. charger and battery.		
Frequency 865 868 MHz (ETSI), standard software preinstalled.		
SIMATIC RF650M (FCC) mobile handheld terminal	6GT2813-0CA10	
Basic unit, suitable for transpon- ders conforming to EPCglobal Class 1 Gen 2 / ISO 18000-6C, incl. charger and battery.		
Frequency 902 928 MHz (FCC), standard software preinstalled.		
Accessories		
Charging/docking station	6GT2898-0BB00	
For one RF650M mobile reader and one spare battery, including Ethernet port, USB port and USB cable.		G FEIG
		Charging/docking station for RF650M mobile handheld terminal
Replacement battery	6GT2898-0CB00	
for SIMATIC RF650M mobile handheld terminal		
DVD "RFID-Systeme Software & Documentation"	6GT2080-2AA20	

SIMATIC RF600 antennas

Introduction

Overview

SIMATIC RF600 UHF antennas are used in many different applications in production, material handling, and logistics. Thanks to their rugged design and high degree of protection, they are also suitable for harsh industrial environments.



RF640A

Features	Page
Particularly compact antenna for applications in production, e.g. assembly lines or conveyor systems.	3/45

Universal and compact standard

antenna for wide ranges

3/48



Page

3/48

RF620A

Overview



The SIMATIC RF620A antenna is characterized by an especially compact enclosure. It is particularly suitable for use in production, e.g. on assembly lines or track-guided conveyor systems. The effects of reflections and overshooting can be reliably reduced thanks to the linear polarization and high degree of signal attenuation.

The antenna can be operated with the UHF readers of the SIMATIC RF600 range.

Technical specifications

Linear

small

Article number	6GT2812-1EA00	6GT2812-1EA01	
Product type designation	BE620A ETSL antenna	RE620A ECC antenna	
Suitability for operation	SIMATIC RE600	SIMATIC BE600	
Wireless frequencies			
Transmission frequency	865 868 MHz	902 928 MHz	
Electrical data			
Impedance	50 Ω	50 Ω	
Polarization	Linear	Linear	
Antenna gain compared to spherical radiator			
 with linear radiation 	-5 dB	-5 dB	
Standing wave ratio (VSWR) maximum	2	2	
Radiating angle of the antenna			
horizontal	100°	130°	
vertical	75°	105°	
Type of electrical connection of the antenna	RP-TNC	RP-TNC	
Design of plug-in connection	male	male	
Mechanical data			
Material	PA 12	PA 12	
Color	Pastel turquoise	Pastel turquoise	
Tightening torque of the screw for securing the equipment maximum	2 Nm	2 Nm	
Mounting distance			
 relating to metal surfaces recommended minimum 	0 m	0 m	
Permitted ambient conditions			
Ambient temperature			
 during operation 	-20 +70 °C	-20 +70 °C	
 during storage 	-40 +85 °C	-40 +85 °C	
 during transport 	-40 +85 °C	-40 +85 °C	
Protection class IP	IP67	IP67	
Shock resistance	according to EN 60068-2-27	according to EN 60068-2-27	
Shock acceleration	500 m/s ²	500 m/s ²	
Schwingbeschleunigung	200 m/s ²	200 m/s ²	

RF620A

Article number	6GT2812-1EA00	6GT2812-1EA01	
Product type designation	RF620A, ETSI antenna	RF620A, FCC antenna	
Design, dimensions and weight			
Width	75 mm	75 mm	
Height	75 mm	75 mm	
Depth	20 mm	20 mm	
Net weight	100 g	100 g	
Mounting type	2 screws M5	2 screws M5	
Cable length of antenna cable	0 m	0 m	
Product properties, functions, components general			
Product feature silicon-free	Yes	Yes	
Standards, specifications, approvals			
Certificate of suitability	CE (ETSI EN 302208)	FCC (Title 47, Part 15.247), cULus	
Accessories			
Accessories	Antenna cables 1 to 40 m	Antenna cables 1 to 40 m	

Selection and ordering data

	Article No.	
SIMATIC RF620A (ETSI)	6GT2812-1EA00	Accessories
Linear polarized UHF antenna for frequency range 865 to 868 MHz.		Note: To ensure optimal functio of the antenna, it is recommend that a Siemens antenna cable
SIMATIC RF620A (FCC) compact antenna	6GT2812-1EA01	Antenna cable
Linear polarized UHF antenna for frequency range 902 to 928 MHz.		UV resistant, reverse TNC, UL certified, impedance 50 Ω
		Matarial: RE, balagan free

Accessories	
Note: To ensure optimal functioning of the antenna, it is recommended that a Siemens antenna cable is used.	
Antenna cable	
UV resistant, reverse TNC, UL certified, impedance 50 Ω	
 Material: PE, halogen-free 	
Con Con	
 Length 1 m, Ø 5 mm, attenuation 0.5 dB 	6GT2815-0BH10
 Length 3 m, Ø 5 mm, attenuation 1 dB 	6GT2815-0BH30
 Length 10 m, Ø 5 mm, attenuation 4 dB 	6GT2815-0BN10
 Length 10 m, Ø 7.6 mm, attenuation 2 dB 	6GT2815-1BN10
 Length 20 m, Ø 7.6 mm, attenuation 4 dB 	6GT2815-0BN20
 Length 40 m, Ø 10.3 mm, attenuation 5 dB 	6GT2815-0BN40
 Material: PVC, Ø 5.5 mm, suitable for cable carriers 	
- 5 m long, 1.5 dB attenuation	6GT2815-2BH50
- 15 m long, 4.5 dB attenuation	6GT2815-2BN15

Article No.

RF620A





SIMATIC RF620A antenna

SIMATIC RF600 antennas

RF640A, RF642A

Overview





6GT

Circular

The SIMATIC RF640A/RF642A are rugged and compact antennas for industrial applications in production and logistics.

- The SIMATIC RF640A is a universal antenna for numerous applications. They are used, in particular, in applications where transponders in widely varying orientations have to be detected.
- The SIMATIC RF642A is, with its linear polarization, particularly suitable for severely metallic environments.



Linear

Both antennas can be used in Europe, the United States and China (broadband) and with the readers of the SIMATIC RF600 range.

•		
Article number	6GT2812-0GA08	6GT2812-1GA08
Product type designation	RF640A antenna	RF642A antenna
Suitability for operation	SIMATIC RF600	SIMATIC RF600
Wireless frequencies		
Transmission frequency	865 928 MHz	865 928 MHz
Electrical data		
Impedance	50 Ω	50 Ω
Polarization	Circular	Linear
Antenna gain compared to spherical radiator		
 with linear radiation 		6 dB
 with circular radiation 	4 dB	
Standing wave ratio (VSWR) maximum	1.5	1.5
Radiating angle of the antenna		
 horizontal 	80°	75°
vertical	75°	70°
Type of electrical connection of the antenna	RP-TNC	RP-TNC
Design of plug-in connection	male	male
Mechanical data		
Material	PA 12	PA 12
Color	Pastel turquoise	Pastel turquoise
Tightening torque of the screw for securing the equipment maximum	2 Nm	2 Nm
Mounting distance		
 relating to metal surfaces recommended minimum 	0 m	0 m

Technical specifications

SIMATIC RF600 antennas

RF640A, RF642A

Article number	6GT2812-0GA08	6GT2812-1GA08
Product type designation	RF640A antenna	RF642A antenna
Permitted ambient conditions		
Ambient temperature		
during operation	-25 +75 °C	-25 +75 °C
during storage	-40 +85 °C	-40 +85 °C
during transport	-40 +85 °C	-40 +85 °C
Protection class IP	IP65	IP65
Shock resistance	according to EN 60068-2-27	according to EN 60068-2-27
Shock acceleration	300 m/s ²	300 m/s ²
Vibrational acceleration	100 m/s ²	100 m/s ²
Design, dimensions and weight		
Width	185 mm	185 mm
Height	185 mm	185 mm
Depth	45 mm	45 mm
Net weight	600 g	600 g
Mounting type 4 screws M4 according to VESA 100, optional with articulated bracket by using antenna mounting kit 4 screws M4 according to VESA 100, optional with articulated bracket by using antenna mounting kit		4 screws M4 according to VESA 100, optional with articulated bracket by using antenna mounting kit
Cable length of antenna cable	0 m	0 m
Product properties, functions, components general		
Product feature silicon-free	Yes	Yes
Standards, specifications, approvals		
Certificate of suitability	CE (according to R&TTE), FCC (Title 47, Part 15.247), cULus	CE (according to R&TTE), FCC (Title 47, Part 15.247), cULus
Accessories		
Accessories	Antenna cables 1 to 40 m, antenna mounting kit	Antenna cables 1 to 40 m, antenna mounting kit

Selection and ordering data

	Article No.		Article No.
SIMATIC RF640A	6GT2812-0GA08	Material: PVC, Ø 5.5 mm, suitable for cable	
for UHF frequency 865 MHz to		carriers	
928 MHz (ETSI, FCC, CMIIT).		- 5 m long, 1.5 dB attenuation	6GT2815-2BH50
SIMATIC RF642A	6GT2812-1GA08	- 15 m long, 4.5 dB attenuation	6GT2815-2BN15
Linear polarization antenna		Antenna mounting kit	6GT2890-0AA00
928 MHz (ETSI, FCC, CMIIT).		For flexible mounting,	
Accessories		with articulated blacket.	
Note:			
To ensure proper functioning of the antennas, it is recommended that Siemens antenna cables are used.			
Antenna cable			
UV resistant, reverse TNC, UL certified, impedance 50 Ω			
 Material: PE, halogen-free 			
Ed the			
 Length 1 m, Ø 5 mm, attenuation 0.5 dB 	6GT2815-0BH10		
 Length 3 m, Ø 5 mm, attenuation 1 dB 	6GT2815-0BH30		
 Length 10 m, Ø 5 mm, attenuation 4 dB 	6GT2815-0BN10		
 Length 10 m, Ø 7.6 mm, attenuation 2 dB 	6GT2815-1BN10		
 Length 20 m, Ø 7.6 mm, attenuation 4 dB 	6GT2815-0BN20		
 Length 40 m, Ø 10.3 mm, attenuation 5 dB 	6GT2815-0BN40		

SIMATIC RF600 antennas

RF640A, RF642A

Dimensional drawings



SIMATIC RF640A, RF642A antennas
RFID systems for the UHF range SIMATIC RF600 antennas

RF660A

Overview



The universal UHF antenna RF660A is suitable for numerous applications in production and logistics that require a greater range. Typical applications are conveyor systems in material handling and logistics systems as well as gates, e.g. in the incoming goods department.

Thanks to its rugged design and high degree of protection, the SIMATIC RF660A antenna is also suitable for harsh industrial environments. The antenna can be operated with the readers of the SIMATIC RF600 range.



Technical specifications

Article number	6GT2812-0AA00	6GT2812-0AA01
Product type designation	RF660A 865-868 EU antenna	RF660A 902-928 US antenna
Suitability for operation	SIMATIC RF600	SIMATIC RF600
Wireless frequencies		
Transmission frequency	865 868 MHz	902 928 MHz
Electrical data		
Impedance	50 Ω	50 Ω
Polarization	Circular	Circular
Antenna gain compared to spherical radiator		
 with circular radiation 	7 dB	6 dB
Standing wave ratio (VSWR) maximum	2	2
Radiating angle of the antenna		
horizontal	60°	70°
vertical	60°	70°
Type of electrical connection of the antenna	RP-TNC	RP-TNC
Design of plug-in connection	male	male
Mechanical data		
Material	PA 12	PA 12
Color	Pastel turquoise	Pastel turquoise
Mounting distance		
 relating to metal surfaces recommended minimum 	0 m	0 m
Permitted ambient conditions		
Ambient temperature		
 during operation 	-25 +75 °C	-25 +75 °C
 during storage 	-40 +85 °C	-40 +85 °C
 during transport 	-40 +85 °C	-40 +85 °C
Protection class IP	IP67	IP67
Shock resistance	according to EN 60068-2-27	according to EN 60068-2-27
Shock acceleration	300 m/s ²	300 m/s ²
Vibrational acceleration	1 m/s ²	1 m/s ²

RFID systems for the UHF range

SIMATIC RF600 antennas

RF660A

Article number	6GT2812-0AA00	6GT2812-0AA01
Product type designation	RF660A 865-868 EU antenna	RF660A 902-928 US antenna
Design, dimensions and weight		
Width	313 mm	313 mm
Height	313 mm	313 mm
Depth	80 mm	80 mm
Net weight	1.6 kg	1.6 kg
Mounting type	4 screws M4 according to VESA 100, optional with articulated bracket by using antenna mounting kit	4 screws M4 according to VESA 100, optional with articulated bracket by using antenna mounting kit
Cable length of antenna cable	0 m	0 m
Product properties, functions, components general		
Product feature silicon-free	Yes	Yes
Standards, specifications, approvals		
Certificate of suitability	CE (ETSI EN 302208)	FCC (Title 47, Part 15.247), cULus
Accessories		
Accessories	Antenna cables 1 to 40 m, antenna mounting kit	Antenna cables 1 to 40 m, antenna mounting kit

Selection and ordering data

	Article No.
SIMATIC RF660A (ETSI) antenna	6GT2812-0AA00
Circular polarized UHF antenna for frequency range 865 to 868 MHz.	
SIMATIC RF660A (FCC) antenna	6GT2812-0AA01
Circular polarized UHF antenna for frequency range 902 to 928 MHz.	

	Article No.
Accessories	
Note:	
To ensure proper functioning of the SIMATIC RF660A antenna, it is recommended that Siemens antenna cables are used	
Antenna cable	
UV resistant, reverse TNC, UL certified, impedance 50 Ω	
Material: PE, halogen-free	
Com Com	
- Length 3 m, Ø 5 mm, attenuation 1 dB	6GT2815-0BH10
 Length 10 m, Ø 5 mm, attenuation 4 dB 	6GT2815-0BH30
 Length 10 m, Ø 7.6 mm, attenuation 2 dB 	6GT2815-0BN10
 Length 20 m, Ø 7.6 mm, attenuation 4 dB 	6GT2815-1BN10
 Length 40 m, Ø 10.3 mm, attenuation 5 dB 	6GT2815-0BN20
 Length 3 m, Ø 5 mm, attenuation 1 dB 	6GT2815-0BN40
 Material: PVC, Ø 5.5 mm, suitable for cable carriers 	
- 5 m long, 1.5 dB attenuation	6GT2815-2BH50
- 15 m long, 4.5 dB attenuation	6GT2815-2BN15
Antenna mounting kit	6GT2890-0AA00
For flexible mounting, with articulated bracket.	

3

RFID systems for the UHF range SIMATIC RF600 antennas

RF660A

Dimensional drawings



SIMATIC RF660A antenna



SIMATIC RF660A antenna, position of connection



Antenna mounting kit

© Siemens AG 2016

RFID systems for the UHF range

Notes



4/2 4/2	Optical identification Introduction
4/6	Stationary code reading systems
4/11	MV420
4/6	MV440
4/32	Lenses
4/37	Handheld reading systems
4/39	MV320
4/41	MV325
4/43	MV340
4/45	Verification systems
4/45	Veri-Genius for MV440
4/50	Optical character recognition (OCR)
4/50	Text-Genius for MV440
4/54	Object recognition
4/54	Pat-Genius for MV440

Introduction

Overview



Optical readers – Reading and verification of 1D/2D codes

For state-of-the-art production systems, tracing products and parts with machine-readable identification is a central requirement. A unique coding system permits the planning and implementation of each and every step of production for every part manufactured as well as changes within the production process or in the materials used. Direct marking of products also allows the implementation of specified legal requirements for tracing production batches throughout the production system.

What is direct part marking (DPM)?

Direct part marking (DPM) is the application of a mark directly on the surface of a product without the use of a separate carrier material, such as an adhesive label. This makes it possible to identify products in production and trace them after delivery as well.

With so-called 2D codes a coding method is available that meets these user requirements. 2D codes consist of easy to implement, point-shaped basic elements. Laser and needle marking technologies are outstanding with regard to durability, marking speed and material independence. Despite mechanical deformations, e.g. with metallic work pieces, the 2D codes can still be read using 2D readers even after multiple processing steps. 2D codes also provide the advantage of being able to encode data in more limited spaces than comparable barcodes or plain text.

Benefits

Designed for Industry get

- · Clear identification of products and product parts
- · Marking in accordance with international standards (e.g. ISO 29158).
- Direct part marking is the key technology for tracing products - low-cost, undetachable, and almost indestructible.
- Flexible and economic solutions thanks to the complete and scalable portfolio of powerful stationary optical readers.
- Simplified engineering, commissioning, diagnostics and maintenance through seamless integration into Totally Integrated Automation (TIA):
- Integrated bus connection to an automation system, such as SIMATIC, SIMOTION or SINUMERIK via communication modules with PROFIBUS and PROFINET.
- Easy S7 software integration based on ready-to-use function blocks.
- Extensive status and diagnostic functions.
- · Greater security of investment due to support of all standard matrix and barcodes.
- Openness due to connection possibilities to different bus systems from different manufacturers and PC environments via communication modules.

Integration

The product range of optical reading devices from Siemens

Stationary optical readers



Stationary optical SIMATIC MV440 and MV420 readers

The high-performance stationary optical readers are small, userfriendly devices for reading applications. The devices read various two-dimensional (2D) codes as well as one-dimensional (1D) barcodes. Optionally, function packages can be added to all SIMATIC MV440 devices using SIMATIC License Manager licenses. The following licenses are available for function expansion:

- Veri-Genius for measuring the marking quality
- Text-Genius for text recognition and
- · Pat-Genius for object recognition

These optional function extensions can be selected and combined as required.

Optical handheld reading devices



SIMATIC MV320 optical handheld reading device



SIMATIC MV325 optical handheld reading device



SIMATIC MV340 optical handheld reader

The high-performance, high-resolution handheld readers are suitable for either two-dimensional (2D) data matrix codes and/or one-dimensional (1D) bar codes. The devices can communicate with a host computer via RS232, USB or Bluetooth, depending on the selected model.

Introduction

Verification systems



Graphical representation of the marking quality (verification) in the user interface

By using verification systems, the readability of marks is guaranteed throughout the entire production process, regardless of any possible contamination or when using different readers. Moreover, the marking can continue to be read after the production process throughout the lifespan of the product.

In addition to reading 1D barcodes and 2D matrix codes, SIMATIC MV440 can be expanded at any time with verification functionality using the "Veri-Genius" verification license. The license is supplied as a "Single License" on a USB stick and can be copied to the SIMATIC MV440 with the SIMATIC Automation License Manager (ALM) using a plug-in. The license is executable on any SIMATIC MV440 as of firmware version 4.0.

Optical character recognition



SIMATIC MV440 HR OCR

With the "Text-Genius" OCR license, SIMATIC MV440 can also be used for optical character recognition (OCR) in addition to reading 1D barcodes and 2D matrix codes. It is also possible to read and compare plain text and machine-readable code in the same image field.

Text recognition is available in two versions. "Text-Genius" is the text recognition version that is supplied ready-to-use for a specified character set (e.g. Polyfont). The "Text-Genius Plus" version is available for any character sets and project-specific character sets. In this version, the recognition can be adapted to numerous character sets and print images by means of project-specific training. Both text recognition licenses include the functionality of "PAT-Genius" for preparing (e.g. searching for the label position) text recognition.

The licenses are supplied as a "Single License" on a USB stick and can be copied to the device with the SIMATIC Automation License Manager (ALM) using a plug-in. The "Text-Genius" license is executable on any SIMATIC MV440 from firmware version 3.0 - the "Text-Genius Plus" license on any SIMATIC MV440 from firmware version 5.0

Object detection



Object recognition with Pat-Genius

With the "Pat Genius" object recognition license, SIMATIC MV440 can also be used for object recognition (object classification, position detection, counting, etc.) in addition to reading 1D barcodes and 2D matrix codes. In addition, the functionality is possible in combination with text recognition, for example, thus enabling position control of a label and control of the labeling (reading and comparison) of plain text in an image field.

The license is supplied as a "Single License" on a USB stick and can be copied to the device with the SIMATIC Automation License Manager (ALM) using a plug-in. The license is executable on any SIMATIC MV440 firmware version 6.0 or higher.

Stationary code reading systems

Introduction

Overview



The stationary optical code readers read various two-dimensional (2D) codes as well as one-dimensional (1D) barcodes. SIMATIC MV440 also features additional functions for measuring the marking quality (verification) for process control purposes, and for text recognition (optical character recognition, OCR) and object detection. All devices can be easily and flexibly integrated into the automation system thanks to standardized, industry-compatible interfaces and function blocks.

SIMATIC MV420

The SIMATIC MV420 series is particularly suitable for close-up to mid-range reading distances (approx. 10 mm to 400 mm).

The SIMATIC MV420 is an optical reader that has been specially designed for detecting and evaluating a variety of machine readable codes in the packaging industry (e.g. F&B, pharmaceuticals and tobacco) and industrial production (e.g. automotive, electronics and solar). The list of readable codes includes all standard matrix codes and barcodes which can be reliably detected - mostly independent of the printing technology applied and carrier medium used. One key feature of the unit is its ability to read data matrix codes (DMC). The SIMATIC MV420 device family is flexible, reliable and easy to use.

Besides this, two different lenses are available for the SIMATIC MV420 which can be adjusted to the required reading distances. In addition, various powerful integrated illumination systems are available. The models can be ordered as preconfigured or freely combinable. The particularly compact enclosures have the high degree of protection IP67.

SIMATIC MV440

The SIMATIC MV440 is an optical reader designed specifically for the recognition and evaluation of numerous machine-readable codes in industrial production. The SIMATIC MV440 device family is characterized by very high reading reliability, highspeed reading and flexible process interfacing. The product is also robust, has a high degree of protection, and is easy to use. The professional decoding software is suitable for almost all types of marking, especially sophisticated "direct part marking", on a wide range of different carrier materials.

With the "Veri-Genius" verification license, the optical MV440 readers are able to verify the marking quality of codes in accordance with the applicable standards. The device determines the quality of the applied code and helps you ensure the readability using the following process steps. Verification can be performed simultaneously with the other functions, e.g. reading of 1D and 2D codes.

With the "Text-Genius / Text-Genius Plus" text recognition licenses, the optical MV440 readers can be used for text recognition (OCR optical character recognition). Text recognition can be performed simultaneously with the other functions, e.g. reading of 1D and 2D codes.

With the "Pat-Genius" object recognition license, object recognition, position detection, presence checks, completeness checks and text recognition (contour-based) are all possible. Object recognition can also be combined with the other functions.

Optical identification

Stationary code reading systems

Introduction

	Ма	ior	dif	fere	end	ces
--	----	-----	-----	------	-----	-----

Optical readers	SIMATIC MV420	SIMATIC MV440	
Housing	Extremely compact design, IP67	Compact design, IP67	
Sensor / resolution	CMOS 640 x 480 pixels 752 x 480 pixels	CCD 640 x 480 pixels 1 024 x 768 pixels 1 600 x 1 200 pixels	
Lens system	Freely selectable lenses (M12) Lens selection: http://www.siemens.com/tia-selection-tool	Freely selectable lenses due to C-Mount lens connection Lens selection http://www.siemens.com/tia-selection-tool	
Lighting	Integrated lighting	Integrated or external lighting	
Commissioning and operation	 Integrated web server Auto-optimizing of parameters Languages: English / German / French / Italian / Spanish / Chinese 	 Integrated web server Auto-optimizing of parameters Languages: English / German / French / Italian / Spanish / Chinese 	
Communication	 PROFIBUS (via communication module; M16) PROFINET (on-board M12 or via communication module, various interfaces) Ethernet (onboard, M12) RS232 (onboard, M16) 	 PROFIBUS (via communication module, M12) PROFINET (on-board M12 or via communication module, various interfaces) Ethernet (onboard, M12) RS232 (onboard, M16) 	
Digital inputs/outputs	1 trigger1 strobe2 programmable inputs/outputs	 1 trigger 1 strobe 4 programmable inputs/outputs	
Optical character recognition	-	Polyfont (can be used without training)Freely trainable fonts	
Object detection	-	Objects/shapes are freely trainable	
Verification	-	 ISO/IEC 29159:2011 (previously: AIM DPM-1-2006) ISO/IEC 16022:2000 ISO/IEC 15415:2004 AS9132 Rev A, 2005 ISO/IEC 15416:2000 ANSI X3.182-1990 	

Application

- Automotive industry
 - Needle punched markings on various automotive power train components (cylinder heads, cylinder blocks, manifolds, etc.)
 - Laser markings on various automotive power train components (camshafts, crankshafts, pistons, connecting rods, transmission components, etc.)
 - Laser markings on electronic components, printed circuit boards, or enclosures
- Packaging (e.g. pharmaceutical, F&B and tobacco industries)
 - Printed or laser markings on folded boxes, plastic containers, etc.
 - Reading through transparent foil packaging
- Aerospace industry
 - Needle punched markings on gas turbine blades
 - Needle punched markings on various aluminum components of propulsion units

- Medical equipment
- Laser markings on pacemakers and other implantable devices
- Laser markings on various medical devices and drugs
- Electronics
 - Laser markings on ESD sensitive hard drive components or even on printed labels
- Semiconductor
 - Laser markings on rigid and flexible circuit boards
 - Laser markings on packaged semiconductor devices, heat sinks or heat dissipators

4

Stationary code reading systems

Introduction

Integration

The SIMATIC MV420/440 readers have industry-standard PROFINET and communication module interfaces on the device. In addition, communications interfaces such as Ethernet and RS232 are directly available on the device.

Via the specified interfaces, the following communication services can be used:

Usable communication services	Interface
PROFINET IO (FB 79)	Onboard MV400 PROFINET interface.
PROFINET IO (FB 101, Ident profile)	Onboard MV400 PROFINET interface.
PROFINET IO (FB 45, FB 101, Ident profile)	Via communication module interface, with communication module RF180C.
Ethernet/IP	Via communication module interface, with communication module RFID 181EIP.
PROFIBUS DP V0/1 (FB 45, Ident profile)	Via communication module interface, with communication module ASM 456.
TCP/IP (HTTP, ASCII)	Onboard MV400 PROFINET interface.
RS232 (ASCII)	Onboard MV400 RS232 interface.
SIMATIC S7-1200, S7-300, ET 200pro	Via communication module interface, with communication module RF120C, RF170C, ASM 475.

The preferred connection of the SIMATIC MV420/440 readers in the SIMATIC environment is the onboard PROFINET interface. The standard function block "Ident Profile" (FB 101) is available for this interface. This type of connection is a component of the device library of SIMATIC TIA Portal, Version 13 SP1 or higher, and is compatible for the connection of communication modules.

Furthermore, the SIMATIC MV420/440 readers are compatible with the predecessor products SIMATIC VS130-2. For this purpose, the onboard PROFINET interface is released for use with function block FB 79.

A separate function block called "LDrivers MV4X0" is available for the connection to SIMOTION systems. You will find additional information on the topic of LDrivers MV4x0 under: http://support.automation.siemens.com/WW/view/en/67385474



Integration of SIMATIC MV420/MV440 with a direct connection to PROFINET or Ethernet, with/without PoE (PLC and HMI via Profinet/Ethernet; trigger via DI)

Stationary code reading systems

Introduction



Integration of SIMATIC MV420/MV440 with connection via RS232 (PLC via RS232; trigger via DI; HMI via Ethernet)

Via the onboard communication module interface, all communication modules can be used, e.g. for the PROFIBUS connection. The communication module interface is compatible with all available communication modules both electrically and with regard to protocol. The connection via a communication module therefore makes it possible to switch between optical code readers and RFID readers, simply by reconnection. The PLC programming is performed with the aid of function blocks that are available for SIMATIC and SIMOTION. A frequently applied integration method is the connection of the SIMATIC MV420/440 readers to the controller (e.g. transmission of the read results) via communication modules. The onboard PROFINET interface is thus available for a separate connection to HMI or a control center.

The advantage of connecting SIMATIC MV420/440 to a communication module is that a wide variety of PLC types and fieldbus systems can be connected. Furthermore, with the communication modules, the complete range of cables of these modules is available. For details on this, see chapter 5 "Communication modules".

Stationary code reading systems

Introduction



Integration of SIMATIC MV420/MV440 by means of the ASM 456 communication module (PLC via Profibus; HMI via Ethernet)



Integration of SIMATIC MV420/MV440 by means of the SIMATIC RF180C communication module (PLC via Profinet; HMI via Ethernet; trigger via DI or RS422)

SIMATIC MV420

Overview

Image: Constraint of the second sec

The SIMATIC MV420 is a particularly compact optical reader and is suitable for close-up to mid-range reading distances (approx. 10 mm to 400 mm).

The optical SIMATIC MV420 reader has been specifically designed for detecting and evaluating a variety of machine readable codes in the packaging industry (e.g. F&B, pharmaceuticals, and tobacco) and industrial production (e.g. automotive, electronics, and solar). The list of readable codes includes all standard matrix codes and barcodes which can be reliably detected - mostly independent of the printing technology applied and carrier medium used. One key feature of the unit is its ability to read data matrix codes (DMC). The SIMATIC MV420 device family is flexible, reliable and easy to use.

Highlights at a glance:

- Compact design with IP67 degree of protection.
- Variety of lenses with variable reading distances.
- Integrated high-performance lighting.
- Web server technology: a normal Web browser is sufficient for parameter assignment.
- Interfaces: Ethernet, PROFINET, RS232, DI/DO, and direct connection to RFID communication modules (ASM).
- Exceptionally high reading speeds, depending on the model.

Further important product characteristics are:

- Excellent read algorithms based on many years of experience in the development and production of optical readers for industrial applications.
- No special knowledge required for reliable parameterization of reading features. Parameterization usually unnecessary, and is only required for difficult to read codes. "Setup" is performed automatically by presenting a readable code pattern.
- Code quality evaluation: Displays the key quality parameters of the code to be read.
- Customized user interface can be easily generated with SIMATIC WinCC flexible/WinCC.

- Web-based user interface; can run on a variety of platforms meeting the following requirements: Internet browser (IE 6.0 or higher), JAVA-VM (MS, SUN).
- Password protected user interface with integrated access rights administration.
- Web-based user interface available for easy integration with an HMI device. The browser and JAVA VM requirements previously mentioned also apply in this case.
- 6 language versions (operator interface, manual and online help are each available in German, English, French, Spanish, Italian, and Chinese).

In addition, SIMATIC MV420 SR-P offers the following highlights:

- Autotrigger mode: Automatic detection of a code without an external trigger signal.
 - Savings in sensor technology and cabling.
 - Reduced potential for error as there are fewer components.
- Solution for applications where proximity switches and light barriers cannot be used
- Open Web API interface for comfortable creation of customized applications and PC-based camera remote control
- Multicode: reads multiple codes in one step within the same field of view.
- ID-Genius: A high-performance code reading algorithm for poorly legible directly marked data matrix codes (DPM: direct part marking).

Application

Key features of the SIMATIC MV420:

- Reading of 1D and 2D codes
- Comparing the read result with a preset value
- · Formatting of read results for further use.

The range of application for the SIMATIC MV420 product family extends to practically all areas of industrial production. The possibilities for use range from identification of stationary parts to fast moving parts on conveyor systems. The powerful integrated lighting allows a very compact design. Due to its high degree of protection (IP67), the device is protected against environmental influences. The optical SIMATIC MV420 reader is therefore suitable for all industrial applications, including direct part marking (DPM). In addition to industrial production, the compact design and flexibility of the optical SIMATIC MV420 reader also make it optimally suitable for the packaging industry (such as for the food and beverage, pharmaceutical and tobacco industries).

The optical readers of the MV420 series include all common communications interfaces, such as Ethernet or PROFINET, and can therefore be connected to a wide variety of systems. An integrated RS422 interface makes it possible to use all of the RFID communication modules, such those required for the PROFIBUS connection. The combination of optical reader and RFID reader is also possible on one communication module.

The reading devices are particularly easy to use and commission despite the wide variety of options for use. Parameters are automatically configured for most applications. If recalibration is required, however, parameter assignment can be carried out conveniently using an Internet browser on the integrated Web server without the need for pre-installed software.

Stationary code reading systems

SIMATIC MV420

Due to the properties and functions described, the emphasis for MV420 is on the following sectors and applications:

- Automotive industry:
 - Needle markings on various drive components (DPM), e.g. cylinder heads, cylinder blocks, manifolds.
 - Laser markings on various power train components (DPM), e.g. camshafts, crankshafts, cylinder piston, connecting rods, gearbox components.
 - Laser markings on electronic components, printed circuit boards, or enclosures.
- Pharmaceutical industry, food industry (F&B), tobacco industry:
 - Printed or laser markings on drugs (DPM, OCR/OCV).
 - Recording the contents of cartons (up to 150 codes).
 - Read portal by linking several cameras.
- Aerospace industry:
 - Needle or laser markings on gas turbine blades (DPM).
 - Needle or laser markings on jet engine components (DPM).
- Medical equipment:
 - Laser markings on heart pacemakers and other implants (DPM).
 - Laser markings on medical devices (DPM).
- Electronics:
 - Needle or laser markings on hard disk components.
 - Laser or etched markings on hard disk components (DPM)
- Semiconductors:
 - Laser markings on rigid and flexible circuit boards (DPM).
 - Laser markings on enclosed semiconductor components, heat sinks or heat exchangers (DPM).

More information is available in the accompanying manual.

Design

SIMATIC MV420 is a particularly compact code reader. The device can be assembled from individual components or ordered as a prefabricated unit. The MV420 is available in two versions:

- Basic model: SIMATIC MV420 SR-B
- Performance model: SIMATIC MV420 SR-P

For the individually configurable models the following individual components are available in addition to the basic units (body):

- Lenses
- Ring lights

The basic units include the protective barrel for the lens.

The preconfigured models include an integrated lens (6 mm, aperture 5.6) and a red ring light including protective barrel.

The following accessories are available for the connection and installation:

- Flexible mounting angle
- Power DIO RS232 cable (M16 connector on open end)
- M12 Ethernet cable (varying lengths)
- Ethernet cable (M12 to RJ45) for commissioning/lab operation (various lengths)
- Special communication module cable for M16 connector (M16 to M12) for connecting to RFID communication modules (ASM). Can be expanded using standard communication module cables, if required.
- Plug-in power supply for demonstration and lab operation (for office environment only)
- CD with installation/operating instructions (supplied with unit)

Further information can be found in the supplied manual.

SIMATIC MV420

4

Function

Key functions of the SIMATIC MV420:

- Reading of 1D and 2D codes
- (see "Overview" and "Area of application")
- Formatting of read results for further use and/or comparison
- · Comparing the read result with a preset value
 - Default setting of the comparison string via one of the serial interfaces (PROFINET (ASM and onboard), PROFIBUS (communication module), RS232).
 - Comparison of the formatted read results with the comparison string
- Individual specification possible with FB 45 per read operation

The functions can be used individually or they can be combined.

The SIMATIC MV420 reads the following codes:

- 1D codes (barcodes):
 - Int. 2/5 (no checksum)
 - Int. 2/5+CS (checksum included)
 - Code 128
 - Code 39 (no checksum)
 - Code 39+CS (checksum included)
 - EAN 13
 - EAN 8
 - UPC-A
 - UPC-E
 - GS1 Databar 14
 - GS1 Databar Stacked
 - GS1 Databar Limited
 - GS1 Databar Expanded
- 2D codes:
 - DMC
 - PDF417
 - QR
 - DotCode
 - Vericode

The SIMATIC MV420 reads codes on many different components and surfaces, e.g.:

- Paper or plastic labels
- Plastic parts
- Circuit boards
- Metallic objects

The optical SIMATIC MV420 reader reads codes applied in many different ways, e.g.:

- Printed
- Dot peened
- Laser
- Stamped
- Bored

Stationary code reading systems

SIMATIC MV420



SIMATIC MV420 field of view dimensions for the 6 mm lens



SIMATIC MV420 field of view dimensions for the 16 mm lens

Further information can be found in the supplied manual.

Integration

Various onboard connection options and convenient function blocks are available for the integration into the automation level.

In the case of SIMATIC MV420, direct connection via PROFINET, Ethernet or RS232 is possible.

In addition, communication modules are available for connection to other bus systems or the shared interface with RFID readers.

For further details on the communication modules, see chapter 5 "Communication modules".



© Siemens AG 2016

Optical identification

Stationary code reading systems

SIMATIC MV420



Integration of the SIMATIC MV420 in the automation environment

Technical specifications

Article number	6GF3420-0AA20	6GF3420-0AA40	6GF3420-0AX20	6GF3420-0AX40
Product type designation	MV420 SR-B code reader	MV420 SR-P code reader	MV420 SR-B code reader (body)	MV420 SR-P code reader (body)
Suitability for operation	1D codes: Int. 2/5, Code 128, Code 39, EAN 13, EAN 8, UPC-A, UPC-E, GS1	1D codes: Int. 2/5, Code 128, Code 39, EAN 13, EAN 8, UPC-A, UPC-E, GS1	1D codes: Int. 2/5, Code 128, Code 39, EAN 13, EAN 8, UPC-A, UPC-E, GS1	1D codes: Int. 2/5, Code 128, Code 39, EAN 13, EAN 8, UPC-A, UPC-E, GS1
	2D codes: DMC, PDF417 (without: Truncated, Micro and Macro), QR (without: Micro and Macro), Vericode	2D codes: DMC, Dot code, PDF417 (without: Truncated, Micro and Macro), QR (without: Micro and Macro), Vericode	2D codes: DMC, PDF417 (without: Truncated, Micro and Macro), QR (without: Micro and Macro), Vericode	2D codes: DMC, Dot code, PDF417 (without: Truncated, Micro and Macro), QR (without: Micro and Macro), Vericode
Schnittstellen				
Type of electrical connection				
 of Industrial Ethernet interface 	M12, d-coded	M12, d-coded	M12, d-coded	M12, d-coded
 of the RS422 interface 	M16, 12-pin, male	M16, 12-pin, male	M16, 12-pin, male	M16, 12-pin, male
 of the RS232 interface 	M16, 12-pin, male	M16, 12-pin, male	M16, 12-pin, male	M16, 12-pin, male
 for supply voltage 	M16, 12-pin, male	M16, 12-pin, male	M16, 12-pin, male	M16, 12-pin, male
 at the digital inputs/outputs 	M16, 12-pin, male	M16, 12-pin, male	M16, 12-pin, male	M16, 12-pin, male
Number of digital inputs	3	3	3	3
Number of digital outputs	3	3	3	3
Design of digital inputs	One high-speed trigger input, 2 opto isolated inputs (NPN, PNP capability) optionally as output	One high-speed trigger input, 2 opto isolated inputs (NPN, PNP capability) optionally as output	One high-speed trigger input, 2 opto isolated inputs (NPN, PNP capability) optionally as output	One high-speed trigger input, 2 opto isolated inputs (NPN, PNP capability) optionally as output
Design of digital outputs	1 fast strobe output for external lighting,	1 fast strobe output for external lighting,	1 fast strobe output for external lighting,	1 fast strobe output for external lighting,
	2 isolated outputs optionally as input, short-circuit-proof, max. 100 mA	2 isolated outputs optionally as input, short-circuit-proof, max. 100 mA	2 isolated outputs optionally as input, short-circuit-proof, max. 100 mA	2 isolated outputs optionally as input, short-circuit-proof, max. 100 mA

Stationary code reading systems

SIMATIC MV420				
Article number	6GF3420-0AA20	6GF3420-0AA40	6GF3420-0AX20	6GF3420-0AX40
Product type designation	MV420 SR-B code reader	MV420 SR-P code reader	MV420 SR-B code reader (body)	MV420 SR-P code reader (body)
Optical data				
Design of image sensor of the camera	CMOS chip, VGA (640 x 480), WVGA (752 x 480)	CMOS chip, VGA (640 x 480), WVGA (752 x 480)	CMOS chip, VGA (640 x 480), WVGA (752 x 480)	CMOS chip, VGA (640 x 480), WVGA (752 x 480)
Type of image capture	Global shutter	Global shutter	Global shutter	Global shutter
Range	10 400 mm	10 400 mm	10 400 mm	10 400 mm
Range Note Mounting type of lens	Adjustable within the range Fixed (M12)	Adjustable within the range Fixed (M12)	Adjustable within the range M12 screw-in lens from list of accessories	Adjustable within the range M12 screw-in lens from list of accessories
Type of light source	Integrated lighting or exter- nal lighting according to accessories list	Integrated lighting or exter- nal lighting according to accessories list	Integrated ring lamp accord- ing to accessories list	Integrated ring lamp accord- ing to accessories list
Image acquisition frequency maximum	50 Hz	80 Hz	50 Hz	80 Hz
Code reading rate maximum	29 1/s	50 1/s	29 1/s	50 1/s
Type of focusing	Manual adjustment on the lens cover	Manual adjustment on the lens cover	Manual adjustment on the lens cover	Manual adjustment on the lens cover
Supply voltage, current consumption, power loss				
Supply voltage				
at DC Rated value	24 V	24 V	24 V	24 V
• at DC	19.2 28.8 V	19.2 28.8 V	19.2 28.8 V	19.2 28.8 V
Consumed current at DC at 24 V				
typical	0.17 A	0.17 A	0.17 A	0.17 A
• maximum	2 A	2 A	2 A	2 A
Buffering time in the event of power failure minimum	0.01 s	0.01 s	0.01 s	0.01 s
Mechanical data				
Material	Die-cast aluminum	Die-cast aluminum	Die-cast aluminum	Die-cast aluminum
Color	petrol blue	petrol blue	petrol blue	petrol blue
Permitted ambient conditions				
Ambient temperature				
 during operation 	0 50 °C	0 50 °C	0 50 °C	0 50 °C
 during storage 	-30 +70 °C	-30 +70 °C	-30 +70 °C	-30 +70 °C
 during transport 	-30 +70 °C	-30 +70 °C	-30 +70 °C	-30 +70 °C
Relative humidity at 25 °C without condensation during operation maximum	95 %	95 %	95 %	95 %
Protection class IP	IP67	IP67	IP67	IP67
Shock resistance	According to IEC 60068-2	According to IEC 60068-2	According to IEC 60068-2	According to IEC 60068-2
Shock acceleration	150 m/s ²	150 m/s ²	150 m/s ²	150 m/s ²
Vibrational acceleration	10 m/s ²	10 m/s ²	10 m/s ²	10 m/s ²
Design, dimensions and weight	50.5	50.5	50.5	50.5
Width	52.5 mm	52.5 mm	52.5 mm	52.5 mm
Depth	20.5 mm	20.5 mm	20.5 mm	20.5 mm
Net weight	0.25 kg	0.25 kg	0.25 kg	0.25 kg
Mounting type	2 x MA scrows	2 x MA screws	2 x M4 screws	2 x MA screws
Product properties, functions,	2 x 1014 3016W3	2 × 1014 3016003	2 x 1014 3016003	2 x 1014 3016W3
Product feature silicon-free	Yes	Yes	Yes	Yes
Display version	4 LEDs	4 LEDs	4 LEDs	4 LEDs
Standards, specifications,				
Certificate of suitability	CE, KCC, F&B suitable, UI	CE, KCC, F&B suitable, UI	CE, KCC, F&B suitable, UI	CE, KCC, F&B suitable, UI
MTBF at 40 °C	95 v	95 v	95 v	95 v
MTBF	95 v	95 v	95 v	95 v
Accessories	,	,		,
Accessories	Mounting brackets, built-in ring lamps, M12 lenses	Mounting brackets, built-in ring lamps, M12 lenses	Mounting brackets, built-in ring lamps, M12 lenses	Mounting brackets, built-in ring lamps, M12 lenses

SIMATIC MV420

Selection and ordering data			
	Article No.		Article No.
SIMATIC MV420 SR-B	6GF3420-0AA20	Cable	
Pre-configured basic model:		IE connecting cable	
Including lens (6 mm, aperture 5.6) and a red ring light, without multi- code and ID-Genius algorithm		for commissioning, service and installation	
SIMATIC MV420 SR-P	6GF3420-0AA40	Prefabricated IE FC TP Trailing cable GP 2 x 2 (PROFINET	
Preconfigured performance model		type C) with M12 plug (D-coded) and IE FC RJ45 plug. IP65/IP67	
Including lens (6 mm, aperture 5.6) and a red ring light, for very fast read rates, with multicode and ID-Genius algorithm		degree of protection.	
SIMATIC MV420 SR-B body	6GF3420-0AX20		
Basic model body:			
Does not include multicode or the ID-Genius algorithm		2 m	6XV1871-5TH20
SIMATIC MV420 SR-P body	6GF3420-0AX40	3 m	6XV1871-5TH30
Performance model body:		5 m	6XV1871-5TH50
For very high read rates; includes multicode reading and		10 m	6XV1871-5TN10
the ID-Genius algorithm		15 m	6XV1871-5TN15
Lens accessories		IE Connecting Cable	
Lens kit 6 mm	6GF3420-0AC00-0LK0	Pre-assembled IF FC TP	
Lens 6 mm, aperture 5.6,		Trailing Cable GP 2 x 2	
		(Proof the 1 type 0) with two 4-pin M12 plugs (D-coded) up to 85 m, IP65/IP67 degree of protection.	
Long kit 16 mm	6052420 0AC00 11 K0	E	
	6GF3420-0AC00-1EK0	W ²	
including protective barrel		0.3 m	6XV1870-8AE30
		0.5 m	6XV1870-8AE50
		1 m	6XV1870-8AH10
		1.5 m	6XV1870-8AH15
		2 m	6XV1870-8AH20
-		3 m	6XV1870-8AH30
Protective barrels for lenses		5 m	6XV1870-8AH50
Protective barrel replacement set	6GF3420-0AC00-2AA0	10 m	6XV1870-8AN10
Contains:		15 m	6XV1870-8AN15
2x protective barrel, 3x O-rings, 8x mounting screws, offset screwdriver		Industrial Ethernet FastConnect plug connector, 2x2, 180° cable outlet	6GK1901-1BB10-2AA0
Built-in ring lights		RJ45 plug connector (10/100 Mbit/s) with rugged metal	
		enclosure and FastConnect technology, for Industrial Ethernet FastConnect cable 2x2.	
Built-in ring lamp, red	6GF3420-0AC00-1LT0		
Built-in ring lamp, white	6GF3420-0AC00-2LT0	For further cables, see Catalog	
Built-in ring lamp, infrared	6GF3420-0AC00-3LT0	IK PI under "Passive network components".	

4

SIMATIC MV420

	Article No.		Article No.
Cable 24 V power supply		Additional accessories	
Power cable, M16 pre-assembled, push-pull.		Industrial Ethernet Switch SCALANCE XB205-3	6GK5205-3BD00-2AB2
		With five 10/100 Mbps RJ45 ports	
		(MM FO SC).	
and state		Description see page 5/28.	
AL OF			
1.5 m	6GF3400-0BH15		
2 m	6GF3400-1BH20		
Power Supply cable DIO-RS232			
M16 assembled on one end,			
open on other end			
		Plug-in power supply (EU, US)	6GF3420-0AC00-1PS0
		For demo and laboratory mode	
Com and the second seco		(office environments only)	
10 m	6GF3440-8BA2		
30 m	6GF3440-8BA4		
Adapter cable for RFID communication modules (ASM)	6GF3420-0AC00-2CB0		
M16 connector (MV420) to			
module); length: 2 m; expandable			
to any length with standard communication module cables.			
a stand and			
interface			
Standard communication module cable for installation.			
pre-assembled connecting cable for ASM 456 BE160C BE170C			
RF180C, and RF182C.			
Size B Martin			
2 m	6GT2891-4FH20		
5 m	6GT2891-4FH50		
10 m	6GT2891-4FN10		
20 m	6GT2891-4FN20		
50 m	6GT2891-4FN50		
All cables with M12 connectors mentioned in the chapter 5 can be			
used on the reader to extend the adapter cable.			
Brackets			
Mounting bracket for	6GF3420-0AC00-1AA0		

30

30

Optical identification

40

35

đ

54

φ

Φ

Stationary code reading systems

SIMATIC MV420

Ð

Φ

15 20 40

↓ ~

G_FS10_XX_00403

Dimensional drawings



SIMATIC MV420 stationary optical reader

<u>↓</u>_]

44

Ø 4,3 40

Ċ

Mounting bracket for SIMATIC MV420 stationary optical reader

Stationary code reading systems

SIMATIC MV440

Overview



SIMATIC MV440 with built-in ring light and D65 protective barrel in plastic (included in the scope of supply)



SIMATIC MV440 with built-in ring light and D65 protective barrel (protective barrel available as accessory)



SIMATIC MV400 with external ring light and D65 protective barrel



The SIMATIC MV440 readers have been specially developed for use in industrial production. The devices offer professional decoding algorithms for machine-readable codes and text recognition in one device for production and logistics. The SIMATIC MV440 device family is characterized by flexibility, reliability and ease of use.

The list of readable codes includes all common matrix and barcodes which, regardless of the printing technology and the carrier medium used, are recognized reliably. A special feature of this device is its ability to read data matrix code (DMC) which is frequently used, especially in production, for direct part marking (DPM) and places the highest demands on the readers.

The operating range of the devices extends from 70 mm close range to 3 000 mm long range. Due to the freely selectable lenses and lighting, the working range as well as implementation in applications with special requirements is almost unrestricted. Integration in industrial automation environments is via standardized fieldbus technology. Open interfaces are also supported.

SIMATIC MV440

Benefits

Get Designed for Industry

Highlights at a glance:

- Compact design with IP67 degree of protection.
- Very high reading reliability and read rates thanks to Siemens decoding algorithms
- Different screen resolutions can be selected specific to the application.
- Flexible adaptation to the application by means of freely selectable lenses and lighting.
- Option of integrated or external high-performance lighting
- Variety of interfaces: Ethernet (PoE), PROFINET (PoE), RS232, DI/DO, communication module interface.
- Many connector technologies, can be used via the communication module.
- Function block for PROFINET/PROFIBUS can be used with SIMATIC and SIMOTION.
- Web-based user interface can be used for parameter assignment and monitoring, without the need for installation.

Further important product characteristics are:

- No special knowledge required for reliable parameterization of reading features. Automatic "setup" by presenting a readable code pattern.
- Autotrigger mode: Automatic detection of a code without an external trigger signal.
 - Savings in sensor technology and cabling.
 - Reduced potential for error as there are fewer components.
 - Solution for applications in which proximity switches and light barriers cannot be used.
- Multicode function: Reads multiple codes in one step within the same field of view.
- ID-Genius: A high-performance reading algorithm for poorly legible directly marked data matrix codes (DPM: direct part marking).
- Code quality evaluation: Displays the key quality parameters of the code to be read.
- Customized user interface can be easily generated with SIMATIC WinCC flexible/WinCC.
- Open Web API interface for comfortable creation of customized applications and PC-based camera remote control
- Web-based user interface; can run on a variety of platforms meeting the following requirements: Internet browser (IE 6.0 or higher), JAVA-VM (MS, SUN).
- Extensive diagnostics functions ensure operation at the maximum read rate.
- User/password-protected operator interface with integrated management of access rights.
- 6 language versions (operator interface, compact manual and online help are each available in English, German, French, Spanish, Italian and Chinese); manual available in 2 language versions (English and German).

Application

The main functions of SIMATIC MV440 are:

- Reading 1D and 2D codes
- Optical character recognition (OCR).
- Object detection.
- Verification (measuring the code quality).
- Comparing the read result with a preset value.
- Formatting of read results for further use.

The application range of the SIMATIC MV440 product family covers all sectors and areas of industrial production and logistics. The possible applications include the identification of stationary parts through to extremely fast moving parts on a conveyor belt. The powerful integrated lighting allows a very compact design. The device has IP67 degree of protection and is therefore suitable for harsh industrial environments.

Due to its particularly powerful lighting, lenses and sensor technology, the MV440 specializes in applications for direct part marking (DPM). Due to the high picture quality, MV440 recommends itself for measuring the marking quality (verification) in the area of DPM.

Due to the properties and functions described, the emphasis for SIMATIC MV440 is on the following sectors and applications:

- Automotive industry:
- Needle punched markings on various automotive power train components (DPM), e.g. cylinder heads, cylinder blocks, manifolds.
- Laser markings on various automotive power train components (DPM), e.g. camshafts, crankshafts, pistons, connecting rods, transmission components.
- Laser markings on electronic components, printed circuit boards, or enclosures.
- Pharmaceutical industry, food industry (F&B), tobacco industry:
- Print or laser markings on medicines (DPM, OCR).
- Recording the contents of cartons (up to 150 codes).
- Read portal by linking several cameras.
- Aerospace industry:
 - Needle or laser markings on gas turbine blades (DPM).
 - Needle or laser markings on jet engine components (DPM).
- Medical equipment:
 - Laser markings on heart pacemakers and other implants (DPM).
 - Laser markings on medical devices (DPM).
- Electronics:
 - Needle or laser markings on hard disk components.
 - Laser or etched markings on hard disk components (DPM)
- Semiconductors:
- Laser markings on rigid and flexible circuit boards (DPM).
- Laser markings on enclosed semiconductor components, heat sinks or heat exchangers (DPM).

Further information can be found in the supplied manual.

Stationary code reading systems

SIMATIC MV440

Design

The SIMATIC MV440 is a compact, stationary optical reader. It consists of one basic unit, which can be configured with other individual components (lens, ring light, filter and protective barrel). This allows the MV440 to be optimally adapted to the application conditions.

The SIMATIC MV440 basic unit is available in three versions. They differ only with regard to the resolution of the CCD sensor and the associated recording speed mode and read rate. All three versions of the basic unit have identical functionality:

- SIMATIC MV440 SR 640 pixels x 480 pixels, 50 full screens/s
- SIMATIC MV440 HR
- 1 024 pixels x 768 pixels, 20 full screens/s
- SIMATIC MV440 UR
- 1 600 pixels x 1 200 pixels, 15 full screens/s

Using the following accessories, the SIMATIC MV440 basic units can be tailored to the requirements of the application and configured. For a detailed listing of the individual accessories, please refer to the section entitled "Accessories":

- Lenses
- Filter
- · Protective barrel for lens
- Ring lights

The following accessories are available for the connection and installation:

- · Flexible mounting plate
- Power DIO RS232 cable (M16 connector on open end)
- M12 Ethernet cable (varying lengths)
- Ethernet cable (M12 to RJ45) for commissioning/lab operation (various lengths)
- Standard cable with M12 plug for connection to communication modules (see Communication modules)
- Plug-in power supply for demonstration and lab operation (for office environment only)
- CD with installation/operating instructions (supplied with unit)

Stationary code reading systems

SIMATIC MV440

The following configurations are recommended for the close or distant ranges:

Configuration for close range	Lenses	Ring lights	Protective barrel for lens
	Mini lens 8.5 mm	The built-in ring light cannot be used (alternative: external mounting of a ring light).	D65 protective barrels for lenses can be used.
	Mini lens 6 mm	Built-in ring lights can be used.	
	Mini lens 12 mm		
	Mini lens 16 mm		
	Mini lens 25 mm		
	Mini lens 35 mm		
	Mini lens 50 mm		
	Mini lens 75 mm		Use of the D65 protective barrel extension for lenses required.
	-		

Configuration for distant range	Lenses	Ring lights	Protective barrel for lens
	Mini lens 6 mm	External ring lights can be used.	D65 protective barrels for lenses
	Mini lens 8.5 mm		can be used.
	Mini lens 12 mm		
	Mini lens 16 mm		
	Mini lens 25 mm		
	Mini lens 35 mm		
	Mini lens 50 mm		
	Mini lens 75 mm	_	Use of the D65 protective barrel

Function

- The main functions of SIMATIC MV440 are:
- Reading 1D and 2D codes
- Verification (requires license "Veri-Genius")
- **Text recognition** (requires license "Text-Genius")
- Object recognition (requires license "Pat-Genius")
- Comparison of the read result with a default value
- Formatting the read result for forwarding

The functions can be used individually or they can be combined.

All functions, including all licenses, are available to the user in demo mode on each version of the MV440. It is therefore possible to test a licensed function at any time. However, the output result is unusable, because one or more characters of the result will be randomly replaced by the '?' character.

Binary results are completely suppressed.

Read

The SIMATIC MV440 reads the following 1D and 2D codes (detailed information can be found in the manual):

- 1D codes (barcodes):
 - Int. 2/5 (with/without checksum)
 - Code 128
 - Code 93
 - Code 39 (with/without checksum)
 - Code 32
 - EAN 13
 - EAN 8
 - UPC-A
 - UPC-E
 - CodaBar
 - GS1 DataBar (Omnidirectional, Stacked, Limited, Expanded)
 - Pharmacode (0° and 180°)
- Postnet
- · 2D codes:
 - Data Matrix Code (ECC 0 200)
 - PDF417 (without: Truncated, Micro and Macro)
 - QR (without: Micro and Macro)
 - DotCode
 - Vericode (demo mode/VeriCode license)

Verification

Verification is the term used for measuring the marking quality of 1D and 2D codes. This additional functionality is subject to license and is available for every SIMATIC MV440 by installing the "Veri-Genius license". The following verification methods are supported:

- ISO/IEC TR29158 (previously AIM DPM-1-2006)
- Siemens DPM
- ISO/IEC 15415
- AS9132 Rev. A (previously IAQG)
- ISO/IEC 15416 (previously ANSI X3.182-1990)

Siemens ID 10 · 2016

Stationary code reading systems

SIMATIC MV440

Optical character recognition

Text recognition is used to detect plain text (Optical Character Recognition: OCR). This additional functionality is subject to license and is available for every SIMATIC MV440 by installing the "Text-Genius license" or the "Text-Genius-Plus License".

Text recognition with the "Text-Genius license" is able to recognize many fonts without training immediately after installation. Particularly suitable fonts are:

- OCR-A
- Semifont M13
- and similar fonts

With the "Text-Genius Plus license", text recognition can be expanded to include numerous fonts, print image versions (e.g. distortions), and special characters. By contrast, this version requires training, but offers almost unlimited potential in expanding the range of characters to be recognized.

Object detection

Object recognition is used for finding and recognizing trained patterns in the picture. This functionality can be used alone or in combination with all other functions mentioned. Accordingly, it has different areas of application: Shape recognition offers the following functionality:

- Object recognition (classification)
- Position detection (position, rotational position, scaling)
- Presence check (object recognition and position check with setpoint specification)
- Completeness check (multiple presence check with setpoint specification)
- Text recognition (based on the contour of any character or symbol). However, shape recognition can also be used in combination with text recognition, for example. In this case, the text recognition read area can track the current position of an object or label.

Note: In demo mode, the full functionality of the devices is available. Testing of a licensed function is therefore possible at any time. However, the output result is unusable, because one or more characters of the result will be randomly replaced by the character '?'. Binary results are completely suppressed.

Integration

Various onboard connection options and convenient function blocks are available for the integration into the automation level.

In the case of SIMATIC MV440, for example, direct connection via PROFINET, Ethernet or RS232 is possible.

In addition, communication modules are available for connection to other bus systems or the shared interface with RFID readers.



SIMATIC MV440

Technical specifications			
Article number	6GF3440-1CD10	6GF3440-1GE10	6GF3440-1LE10
Product type designation	MV440 SR code reader	MV440 HR code reader	MV440 UR code reader
Suitability for operation	1D codes: Int. 2/5, Code 128, Code 93, Code 39, Code 32, EAN 13, EAN 8, UPC-A, UPC-E, GS1, Pharmacode, Postnet	1D codes: Int. 2/5, Code 128, Code 93, Code 39, Code 32, EAN 13, EAN 8, UPC-A, UPC-E, GS1, Pharmacode, Postnet	1D codes: Int. 2/5, Code 128, Code 93, Code 39, Code 32, EAN 13, EAN 8, UPC-A, UPC-E, GS1, Pharmacode, Postnet
	2D codes: DMC, Dot code, PDF417 (without: Truncated, Micro and Macro), QR (without: Micro and Macro), Vericode	2D codes: DMC, Dot code, PDF417 (without: Truncated, Micro and Macro), QR (without: Micro and Macro), Vericode	2D codes: DMC, Dot code, PDF417 (without: Truncated, Micro and Macro), QR (without: Micro and Macro), Vericode
	Text recognition: OCR-A, Semifont M13, similar fonts	Text recognition: OCR-A, Semifont M13, similar fonts	Text recognition: OCR-A, Semifont M13, similar fonts
	Code verification: ISO/IEC 29158, Siemens DPM, ISO/IEC 15415, AS9132 Rev. A, ISO/IEC 16416	Code verification: ISO/IEC 29158, Siemens DPM, ISO/IEC 15415, AS9132 Rev. A, ISO/IEC 16416	Code verification: ISO/IEC 29158, Siemens DPM, ISO/IEC 15415, AS9132 Rev. A, ISO/IEC 16416
Schnittstellen			
Type of electrical connection			
 of Industrial Ethernet interface 	M12, d-coded, PoE	M12, d-coded, PoE	M12, d-coded, PoE
 of the RS422 interface 	M12, 8-pin, male	M12, 8-pin, male	M12, 8-pin, male
 of the RS232 interface 	M16, 12-pin, male	M16, 12-pin, male	M16, 12-pin, male
 for supply voltage 	M16, 12-pin, male	M16, 12-pin, male	M16, 12-pin, male
 at the digital inputs/outputs 	M16, 12-pin, male	M16, 12-pin, male	M16, 12-pin, male
Number of digital inputs	5	5	5
Number of digital outputs	5	5	5
Design of digital inputs	1 high-speed trigger input	1 high-speed trigger input	1 high-speed trigger input
	4 opto isolated inputs (NPN, PNP capability) optionally as output	4 opto isolated inputs (NPN, PNP capability) optionally as output	4 opto isolated inputs (NPN, PNP capability) optionally as output
Design of digital outputs	1 fast strobe output for external lighting	1 fast strobe output for external lighting	1 fast strobe output for external lighting
	4 isolated outputs optionally as input, short-circuit-proof, max.100 mA	4 isolated outputs optionally as input, short-circuit-proof, max.100 mA	4 isolated outputs optionally as input, short-circuit-proof, max.100 mA
Optical data			
Design of image sensor of the camera	CCD chip 1/3", 640 x 480	CCD Chip 1/3", 1 024 x 768	CCD chip 1/1.8", 1 600 x 1 200
Type of image capture	Global shutter with manual or automatic exposure time	Global shutter with manual or automatic exposure time	Global shutter with manual or automatic exposure time
Range	70 3 000 mm	70 3 000 mm	70 3 000 mm
Range Note	Using C-mount lenses and lens accessories, the range can be exactly matched to the application	Using C-mount lenses and lens accessories, the range can be exactly matched to the application	Using C-mount lenses and lens accessories, the range can be exactly matched to the application
Mounting type of lens	C mount lens connection with Plexiglas lens protection, 65 mm diameter	C mount lens connection with Plexiglas lens protection, 65 mm diameter	C mount lens connection with Plexiglas lens protection, 65 mm diameter
Type of light source	Integrated lighting or external lighting according to accessories list	Integrated lighting or external lighting according to accessories list	Integrated lighting or external lighting according to accessories list
Image acquisition frequency maxi- mum	80 Hz	30 Hz	25 Hz
Code reading rate maximum	80 1/s	30 1/s	25 1/s
Type of focusing	Manual adjustment on the lens	Manual adjustment on the lens	Manual adjustment on the lens
Supply voltage, current consumption, power loss			
Supply voltage			
 at DC Rated value 	24 V	24 V	24 V
• at DC	19.2 28.8 V	19.2 28.8 V	19.2 28.8 V
Consumed current at DC at 24 V			
typical	0.27 A	0.27 A	0.27 A
• maximum	2 A	2 A	2 A
Buffering time in the event of power failure minimum	0.01 s	0.01 s	0.01 s
Mechanical data			
Material	Die-cast aluminum	Die-cast aluminum	Die-cast aluminum
Color	petrol blue	petrol blue	petrol blue
	1		

Stationary code reading systems

SIMATIC MV440 Article number 6GF3440-1CD10 6GF3440-1GE10 6GF3440-1LE10 MV440 SR code reader MV440 HR code reader MV440 UR code reader Product type designation Permitted ambient conditions Ambient temperature 0 ... 50 °C 0 ... 50 °C 0 ... 50 °C during operation during storage -30 ... +70 °C during transport Relative humidity at 25 °C without 95 % 95 % 95 % condensation during operation maximum Protection class IP IP67 IP67 IP67 Shock resistance According to IEC 60068-2 According to IEC 60068-2 According to IEC 60068-2 Shock acceleration 100 m/s² 100 m/s² 100 m/s² Vibrational acceleration 10 m/s² 10 m/s² 10 m/s² Design, dimensions and weight Width 68 mm 68 mm 68 mm Height 122 mm 122 mm 122 mm Depth 45 mm 45 mm 45 mm Net weight 0.55 kg 0.55 kg 0.55 kg Mounting type 4 x M4 screws 4 x M4 screws 4 x M4 screws Product properties, functions, components general Product feature silicon-free Yes Yes Yes Display version 5 LEDs 5 LEDs 5 LEDs Standards, specifications, approvals CE, KCC, F&B suitable, UL CE, KCC, F&B suitable, UL CE, KCC, F&B suitable, UL Certificate of suitability MTBF at 40 °C 88 y 88 y 88 y MTBF 88 y 88 y 88 y Accessories Accessories Licenses (verification and Licenses (verification and Licenses (verification and text recognition), mounting brackets, built-in ring lights, external ring lights, text recognition), mounting brackets, built-in ring lights, external ring lights, text recognition), mounting brackets, built-in ring lights, external ring lights,

C-mount lenses,

protective barrels for lenses

C-mount lenses,

protective barrels for lenses

C-mount lenses,

protective barrels for lenses

SIMATIC MV440

Selection and ordering data

	Article No.		Article No.
SIMATIC MV440 SR	6GF3440-1CD10	Accessories	
For one- and two-dimensional codes. Optional: Text recognition (OCR), object detection and verification of barcodes and data matrix codes. Variable image field and distance.		C-mount lenses Mini lenses with fixed focal length, adjustable aperture and focus (see "Lenses" section on page 4/32).	
Resolution: 640 x 480 pixels. PoE; IP67 using protective barrel for lens and sealing caps, otherwise IP40; pack- age comprises reader, CD and plastic protective barrel for lens.			
SIMATIC MV440 HR	6GF3440-1GE10	in as	
For one- and two-dimensional codes. Optional: Text recognition (OCR), object detection and verification of barcodes and data matrix codes. Variable image field and dictorace		Intermediate ring sets	
Resolution: 1 024 x 768 pixels.		for utilizing mini lenses for close-range macro photography	
PoE; IP67 using protective barrel for lens and sealing caps, otherwise IP40; pack- age comprises reader, CD and plastic protective barrel for lens.		(see "Lenses" section on page 4/32). Filters for utilizing mini lenses (see "Lenses" section on page 4/32)	
SIMATIC MV440 UR	6GF3440-1LE10	Protective barrels for lenses	
For one- and two-dimensional codes. Optional: Text recognition (OCR), object detection and verification of barcodes and data matrix codes. Variable image field and distance. Resolution: 1 600 x 1 200 pixels		D65 protective barrel for lens made of metal, for built-in ring lights, internal diameter 57 mm, max. Lens length 57 mm, IP67 degree of protection.	
PoE; IP67 using protective barrel for lens and sealing caps, otherwise IP40; pack- age comprises reader, CD and plastic protective barrel for lens.			
Optional software modules			
Text recognition module "Text-Genius"	6GF3400-0SL01		
License for the module "Text-Genius", supplied on USB flash drive; executable on SIMATIC MV440 firmware V3.0 and higher (MV440 not included in the scope of supply). For a description, see page 4/50.		Glass front pane Plastic front pane D65 protective barrel for lens made of plastic: to achieve IP67	6GF3440-8AC11 6GF3440-8AC21 6GF3440-8AC12
Text recognition module	6GF3400-1SL01	degree of protection; suitable for all variants of MV440 and for use with	
License for the module "Text-Genius Plus", supplied on USB flash drive; executable on SIMATIC MV440 firmware V5.0 and higher (MV440 not included in the scope of supply). For a description, see page 4/50.		built-in ring lights; max. internal diameter 55 mm, max. lens length 48 mm.	
Verification module "Veri-Genius"	6GF3400-0SL02		
License for the module "Veri-Genius", supplied on USB flash drive; executable on SIMATIC MV440 firmware V4.0 and higher (MV440 not included in the scope of supply).		D65 protective barrel extension	6GE3440-8AC13
For a description, see page 4/45.	0050400.001.00	for lens	
"Pat-Genius" "Pat-Genius" License for the module "Pat-Genius", supplied on USB flash drive; executable on SIMATIC MV440 firmware V6.0 and higher (MV440 not included in the scope of supply). For a description, see page 4/54.	6GF3400-03L03	made of metal, for built-in ring lights, internal diameter 55 mm, extension by 35 mm (cascadable), IP67 degree of protection.	

SIMATIC MV440

	Article No.	· · · · · · · · · · · · · · · · · · ·	Article No.
Built-in ring lights		Cables	
		IE connecting cable M12-180/IE FC RJ45 plug-145 for commissioning, service and installation Prefabricated IE FC TP trailing cable GP 2 x 2 (PROFINET type C) with M12 plug (D-coded) and IE FC RJ45 plug, IP65/IP67 degree of protection.	
• Built-in ring light, red Light source: LED red (630 nm) Flash duration 20 µs to 10 ms, range of illumination 800 mm, mounting materials included, IP67 degree of protection when using protective barrel for lens.	6GF3440-8DA11	2 m	6XV1871-5TH20
• Built-in ring light, white Light source: White LED (440 nm to 650 nm) Flash duration 20 µs to 10 ms, range of illumination 800 mm, mounting materials included, IP67 degree of protection when using protective barrel for lens.	6GF3440-8DA21	3 m 5 m 10 m 15 m IE connecting cable M12-180/M12-180	6XV1871-5TH30 6XV1871-5TH50 6XV1871-5TN10 6XV1871-5TN15
• Built-in ring light, green Light source: Green LED (500 nm to 570 nm) Flash duration 20 µs to 10 ms, range of illumination 800 mm, mounting materials included, IP67 degree of protection when using protective barrel for lens	6GF3440-8DA31	Pre-assembled IE FC IP trailing cable GP 2 x 2 (PROFINET type C) with two 4-pin M12 connectors (D-coded) up to max. 85 m, IP65/IP67 degree of protection, RJ45 assembly possible with plug-in connector 6GK1 901-1BB10-2AA0 (see below).	
• Built-in ring lamp, infrared Light source: Infrared LED (850 nm to 880 nm) Flash duration 20 µs to 10 ms, range of illumination 800 mm, mounting materials included, IP67 degree of protection	6GF3440-8DA41	0.3 m	6XV1870-8AE30
when using protective barrel for lens.		0.5 m	6XV1870-8AE50
External ring lights		1 m	6XV1870-8AH10
- 30		1.5 m	6XV1870-8AH15
and a start of a		2 m	6XV1870-8AH20
3		3 m	6XV1870-84H30
9		5 m	6XV1870-8AH50
1000 m		10 m	6XV1870-8AN10
No. 2		15 m	6XV1870-8AN15
• Ring light, metal, infrared, clear light source LED infrared, light source 850 nm, light source 500 mm to 23 000 mm, suitable for D65 lens protective barrel, supply voltage: 24 V (18 V 30 V), dimensions B x H x T (mm): 142 x 142 x 42.4, degree of protection IP67.	6GF3400-0LT01-7BA1	Industrial Ethernet FastConnect plug connector, 2x2, 180° cable outlet RJ45 plug connector (10/100 Mbit/s) with rugged metal enclosure and FastConnect connection method. For Industrial Ethernet FastConnect cable 2x2.	6GK1901-1BB10-2AA0
 Ring light, metal, red, clear light source LED infrared, light source 500 mm to 3 000 mm, suitable for D65 lens protective barrel, supply voltage: 24 V (18 V 30 V) dimensions W x H x D (mm): 142 x 142 x 42.4, degree of protection IP67. 	6GF3400-0LT01-8DA1	For further cables, see Catalog IK Pl under "Passive network components".	

4

SIMATIC MV440

	Article No.		Article No.
Cable for communication module		Mounting accessories	
Interface Communication module cable for connection to communication modules, e.g. ASM 456, RF160C, RF170C, RF180C, and RF182C. Plug-in cable pre-assembled for SIMATIC MV440.		Reader mounting plate Dimensions W x H x D (mm) 80 x 80 x 60, plate thickness: 4 mm	6GF3440-8CA
COMP DIMENT			
2 m	6GT2891-4FH20		
5 m	6GT2891-4FH50		
10 m	6GT2891-4FN10	Mounting plate for external ring lights	6GF3440-8CD01
20 m	6GT2891-4FN20	Dimensions W x H x D (mm) 96 x 76 x 46, plate thickness: 4 mm	
50 m	6GT2891-4FN50	-	
All cables with M12 connectors men- tioned in the chapter 5 can be used on the reader to extend the adapter cable.			
Cable 24 V power supply		-	
Power cable, M16 pre-assembled, push-pull.			
and a state		Support system, tri-plate Dimensions W x H x D (mm) 80 x 80 x 60, plate thickness: 4 mm	6GF9002-7AD
1.5 m	6GF3400-0BH15	23	
2 m	6GF3400-1BH20	a	
Power IO RS232 cable, MIG prefabri- cated at one end, other end open.		Additional accessories	
10 m	6GF3440-8BA2	SCALANCE X108PoE	6GK5108-0PA00-2AA3
30 m	6GF3440-8BA4	Industrial Ethernet Switch	
Cable for external ring lights Suitable for 6GF3400-0LT01-7BA1, 6GF3400-0LT01-8DA1; M12, open end, 4-pole, not suitable for drag cables, cable connects external ring lights with the control cabinet (24 V, GND, strobe), length 10 m.	6GF3440-8BC4	With 6 x 10/100 Mbps RJ45 ports, electrical 2 x 10/100 Mbps RJ45 PoE ports, electrical. For connecting the MV440 via Power-over-Ethernet (PoE). See also page 5/29.	
Adapter cable for external ring lights Suitable for 6GF3400-0LT01-7BA1, 6GF3400-0LT01-8DA1; enables direct connection of external ring lights to the MV440 when using power supply cable DIO-RS232 (see above). M16, 12-pin socket; M16, 12-pin socket; M12, 4-pin socket, length 25 cm.	6GF3440-8BD1		

Stationary code reading systems

SIMATIC MV440

Dimensional drawings



SIMATIC MV440 stationary optical reader



Protective barrel for lens D65



Protective barrel extension for lens D65



Mounting bracket for the SIMATIC MV440 optical reader



G_FS10_XX_90527

Mounting plate for external ring light



Plexiglas protective barrel

SIMATIC MV440



MV400 ring light

Stationary code reading systems

Lenses

Overview



With a lens suitable for the respective image evaluation task, the size of the image field is determined for the camera image for the required operating distance.

High light intensity and the geometry of the image are extremely important for image evaluation (code reading, form recognition and position detection) High light intensity permits short shutter speeds and consequently a reduction of the blurring due to motion as well as maximizing the range.

Lenses with fixed focal length and a settable aperture and focus are ideal for this purpose and are therefore preferred.

Application

Code reading and text recognition

The algorithms of code reading and text recognition tolerate variations in form and size of the marking. In many applications, optical readers must tolerate the influence of perspective distortion. Geometric errors resulting from the imaging often reduce the reading performance of the overall system.

Important selection criteria for the lenses of readers are fast shutter speeds which guard against blurring due to motion, as well as maximization of the reading distance.

All lenses in this accessories list meet the requirements for code reading and text recognition. In addition, lens accessories (e.g. filters) are available which in conjunction with the accessories of the readers support project-specific configurations.

Form recognition and position location

For form recognition with high reproducibility, is a format-filling high-resolution image is required. Geometric errors resulting from the imaging often reduce the reading performance of the overall system.

Important selection criteria for the lenses of readers are a short exposure time, which guards against blurring due to motion, as well as maximization of the range. It is particularly important to maximize the range, since the stability of image analysis rises as the angle of the image field reduces. This is why a large distance from the test object is advantageous.

All lenses in this accessories list meet the requirements for shape recognition. In addition, lens accessories (e.g. filters) are available which in conjunction with the accessories of the readers support project-specific configurations.

Function

Image types

The optical path of the lens is defined by its construction.

For **spherical lenses** the solid angle depends on the focal length, focus adjustment, and aperture. All rays run through the focal point of the lens (central projection). Objects that are further away from the lens are depicted smaller. Objects that are closer to the lens are depicted larger:



The required image field size (height and width of the image), the size of the sensor chip and the focal length of the lens determine the operating distance:

A = (f x BF) / b

- d = Operating distance (distance from lens to test object) in mm
- f = Focal length of the lens in mm
- IS = Size of image in the plane of the test object in mm
- b = effective dimensions of the sensor in mm

In the case of lenses used in image processing systems, the focal length is fixed, whereas apertures and focus settings can be fixed. The focal length, the maximum focal aperture and the focusing range are normally specified on the lenses.

Focal distance

The focal length makes a statement about the angle of the image field or the ratio of the size of the real object to the size of the image.

The focal length of the lens is determined by the size of the required image field and the size of the camera chip when a specific distance has to be maintained. The most common chip sizes in cameras today are $\frac{1}{2}$ ", $\frac{1}{3}$ " and $\frac{1}{4}$ ". If the distance to the object lies below the adjustable focusing range of the lens, i.e. at close range, the focus can be adjusted using intermediate rings.

Aperture

Reduction of the light intensity by interrupting the optical path.

Focus

Setting the focus of the lens to a specific distance.

Depth of field

Depth of field is the area within which (in front of and behind the object) that is displayed with sufficient sharpness of focus. The larger the aperture (the smaller the aperture number), the smaller the depth of field.

Lenses with a larger focal length have a smaller depth of field, the effect is considerable for images at close range.
Lenses

Lens types

Lenses with smaller focal length are called wide-angle lenses, they can also be used at short operating distances, but produce intense distortion of the image. At a suitable given distance, they have a large image field.

Lenses with a long focal length are called telephoto lenses. They have a large magnification but cannot be focused at close range. So macro lenses are used that can be focused by means of large telescopic extensions or intermediate rings. At a given distance, they have a small image field.

In the case of telecentric lenses, at least the optical path at the object end is almost parallel (parallel projection). This means that objects at different distances are depicted in the same size.

Objects can, however, only be displayed that are smaller than the diameter of the lens. It is not possible to adjust the range of focus with these lenses.

The optical characteristics can be restricted by means of optical filter glasses to counteract distortion in the image. Colored filters limit the spectral range, gray filters limit the light intensity and polarization filters restrict the transmission plane. Filters of this type can be attached either by using the internal thread or the flange on the front of the lens. The holder for the filter glass is designed to fit the lens.

Selection and ordering data

	Article No.
C-mount lenses	
With fixed focal length, adjustable aperture and focus, with locking screw.	
• Mini lens 6 mm, 1:1.4 D = 32 mm, L = 37.5 mm, MOD = 0.1 m ¹⁾	6GF9001-1BB01
• Mini lens 8.5 mm, 1:1.5 D = 42 mm, L = 47 mm; successor type for 6GF9001-1BE; MOD = $0.2 \text{ m}^{1)}$ Not for use with internal ring lamps.	6GF9001-1BE01
• Mini lens 12 mm, 1:1.4 D = 29.5 mm, L = 35.7 mm; MOD = 0.25 m ¹⁾	6GF9001-1BL01
• Mini lens 16 mm, 1:1.4 D = 29.5 mm, L = 37.2 mm; successor type for 6GF9001-1BF; MOD = 0.25 m ¹⁾	6GF9001-1BF01
• Mini lens 25 mm, 1:1.4 D = 29.5 mm, L = 38.9 mm; successor type for 6GF9001-1BG; MOD = 0.25 m ¹⁾	6GF9001-1BG01
• Mini lens 35 mm, 1:1.6 D = 29.5 mm, L = 41.4 mm; MOD = 0.4 m ¹⁾	6GF9001-1BH01
• Mini lens 50 mm, 1:2.8 D = 29.5 mm, L = 38.0 mm; successor type for 6GF9001-1AH; MOD = 0.9 m ¹⁾	6GF9001-1BJ01
• Mini lens 75 mm, 1:2.8 D = 34.0 mm, L = 63.6 mm; MOD = 0.7 m ¹) Not for use with internal ring lamps. If protective tube D60 is used, this lens also requires the protective tube extender (6GF3440-8AC13) which is to be ordered separately.	6GF9001-1BK01
CS-Mount for C-Mount adapter ring 5 mm	6GF9001-1AP02

¹⁾ MOD = Minimum object distance of the lens – please take the influence of any protective tube into account.

Optical identification Stationary code reading systems

Lenses

	Article No.
Accessories for utilizing mini lenses at close range	
Set of intermediate rings with 0.5 mm, 1.0 mm, 5.0 mm, 10.0 mm, 20.0 mm and 40 mm rings with 31 mm diameter C thread, to be screwed in between the lens and the camera body for image capture in the macro range.	6GF9001-1BU
Illustrations are approximate	
Set of intermediate rings with 0.5 mm rings with 31 mm diameter C thread, to be screwed in between the lens and the camera body for image capture in the close range.	6GF9001-18001
Accessories for utilizing mini lenses in the telephoto range	
Focal length doubler D = 30.5 mm, L = 17.9 mm, with C-thread to be screwed in between the lens and camera to extend the focal length by a factor of 2.	6GF9001-1BV
Suitable lenses: 6GF9001-1BE01,1BL01,1BF01,1BG01,1BH01,1BJ01,1BK0	
Filter for utilizing the mini lenses in the limited field of view	
Infrared filter Function: Visible light is largely or completely filtered out, infrared light can pass through. Application: When used with infrared lamps, it is possible to achieve independence from daylight. Suitable lenses: 6GF9001-1BL01,1BF01,1BG01,1BH01,1BJ01	6GF9001-2AD
Blue filter	6GF9001-2AE
Function: Blue light can pass through. Application: e.g. to improve the visualization of structures. Suitable lenses: 6GE9001-1BL011BF011BG011BH011BJ01	
Polarization filter	6GF9001-2AF
Function: Filters out light which is directed at right angles to the polarization direction of the filter. Application: e.g. to reduce reflections from metal.	
Suitable lenses: 6GF9001-1BL01,1BF01,1BG01,1BH01,1BJ01	
Daylight filter Function: Visible light can pass largely undiminished, and frequencies above and below (infrared light and ultraviolet light) are filtered out	6GF3440-8EA1
Application: The filter is used to protect the image sensor in the camera from laser light to the extent that this is outside the visible spectrum.	
Suitable lenses: 6GF9001-1BL01,1BF01,1BG01,1BH01,1BJ01	

Stationary code reading systems

Lenses

Dimensional drawings

Lenses for code reading, text recognition, and object detection







Lens 6GF9001-1BE01



Lens 6GF9001-1BK01



Lens 6GF9001-1BF01



Lens 6GF9001-1BG01



Lens 6GF9001-1BH01



Lens 6GF9001-1BJ01



Lens 6GF9001-1BL01

Stationary code reading systems

Lenses

Accessories for lenses



Focal range doubler 6GF9001-1BV





Overview

Optical handheld readers are suitable for portable reading of two-dimensional (2D) data matrix codes and one-dimensional (1D) barcodes. The integrated complex image processing functions and illumination technologies enable codes to be read on a variety of surfaces. Optical handheld readers of various performance classes are available for this purpose.

The range extends from devices for simple reading tasks such as printed barcodes up to models for demanding, weak-contrast markings such as dot-peened or lasered codes.



SIMATIC MV320

The SIMATIC MV320 handheld reader is the entry level device. It is suitable for labels with higher contrasts, but it can also be used application-specifically for labels with lower contrasts.

The SIMATIC MV320 is also available as a wired version (RS232, USB). The reader is designed for a distance of up to 375 mm.

SIMATIC MV320 optical handheld reader



SIMATIC MV325

The optical SIMATIC MV325 handheld reader is a high-performance reader with Bluetooth wireless communication. It is suitable for labels with higher contrasts, but it can also be used application-specifically for codes with lower contrasts.

The SIMATIC MV325 is supplied with a charging station containing the respective access point of the wireless interface and a cabled connection to the host (USB). The reader is designed for a distance of up to 375 mm.

SIMATIC MV325 optical handheld reader



SIMATIC MV340

The SIMATIC MV340 is the most powerful device and is particularly suitable for demanding applications such as low-contrast and damaged codes. It has a high reading rate when decoding data matrix symbols.

The special integrated lighting works equally well on smooth, reflective or wavy surfaces. The SIMATIC MV340 can be connected via RS232 or USB. This optical handheld reader is designed for close ranges and records codes at a distance of up to 50 mm.

SIMATIC MV340 optical handheld reader

Handheld reading systems

Introduction

Major differences

Туре	SIMATIC MV320	SIMATIC MV325	SIMATIC MV340
Graphic display	-	-	-
Read quality of low-contrast codes	+	+	+++
Operating distance			
 Minimum (code-dependent) 	50 mm (1.9")	50 mm (1.9")	0 mm (0.0")
 Maximum (code-dependent) 	375 mm (14.8")	375 mm (14.8")	50 mm (2.0")
Field of view			
• Near	25 mm x 15 mm (0.98" x 0.6") at 50 mm (1.9") distance	25 mm x 15 mm (0.98" x 0.6") at 50 mm (1.9") distance	36 mm x 29 mm (1.4" x 1.1") at distance of 0 mm (0.0")
• Distant	150 mm x 90 mm (5.9" x 3.5") at 50 mm (1.9") distance	150 mm x 90 mm (5.9" x 3.5") at 375 mm (14.8") distance	71 mm x 57 mm (2.8" x 2.2") at distance of 51 mm (2.0")
Decoding capability	1D: Codabar, Code 11, Code 32, Code 39, Code 93, Code 128, Interleaved 2 of 5, GS1 DataBar (RSS), Maxtrix 2 of 5, MSI Plessey, Plessey, Straight 2 of 5, Trioptic, UPC/EAN/JAN	1D: Codabar, Code 11, Code 32, Code 39, Code 93, Code 128, Interleaved 2 of 5, GS1 DataBar (RSS), Maxtrix 2 of 5, MSI Plessey, Plessey, Straight 2 of 5, Trioptic, UPC/EAN/JAN	1D: Code 39, Code 93, Code 128, I2of5, Codabar, UPC/EAN, Pharmacode, BC 412 2D: Data Matrix, QR Code, MicroQR Code, PDE417, CS1 Databar, Aztec
	Stacked 1D: GS1 Composite (CC-A/CC-B/CC-C), MicroPDF, PDF417	Stacked 1D: GS1 Composite (CC-A/CC-B/CC-C), MicroPDF, PDF417	
	2D: Aztec Code, Data Matrix, Micro QR Code, QR Code, Han Xin	2D: Aztec Code, Data Matrix, Micro QR Code, QR Code, Han Xin	
Department of Defense Unique Identifier String Validator	-	-	•
Code creation	Print, laser	Print, laser	Laser, print, dot peen
Radio interfaces	-	Bluetooth	-
Ports	USB, RS232	USB	USB, RS232

Benefits

G G get Designed for Industry

- Industry leading reading performance for Data Matrix codes, also for hard-to-read DPMs.
- Rugged design, for production environment.
- Supports multiple communication protocols: RS232 / USB or Bluetooth.
- Can read barcodes, data matrix codes, and other symbols.
- Can be used as a replacement device for existing barcode readers.

Application

The optical handheld readers are suitable for optical identification of objects using 1D or 2D codes in the production, logistics, quality assurance, and maintenance and servicing fields. Application examples:

- Automotive industry
 - Markings on various drive components (cylinder heads, cylinder blocks, elbow joints, etc.)
 - Laser markings on various drive components (cam shafts, crankshafts, pistons, piston rods, gearbox components, etc.)
 - Laser markings on electronic components, printed circuit boards, or enclosures
- Mechanical engineering
- Markings on different types of component
- Tobacco industry
 - Printed or laser markings on boxes
- Food industry
 - Printed or laser markings on cartons
 - Laser markings on production machines

Design

All handheld readers are equipped with a handle. The handles are equally suitable for right-handed or left-handed persons. The read process is triggered by a switch on the handle. The handle can be removed. On cabled connections via RS232 or USB, data and power are transmitted direct via the shared cable.

Optical identification Handheld reading systems

SIMATIC MV320

Overview





SIMATIC MV320 is a rugged, powerful industrial barcode and data matrix code reader suitable for high resolutions. This handheld reader reads two-dimensional (2D) data matrix codes and one-dimensional (1D) barcodes.

It can read medium to high contrast data matrix codes. The cell size should be larger than 0.13 mm. Barcodes can be read if the width of a bar is larger than 0.12 mm.

The reader possesses complex image processing functions and illumination technology in order to read codes on many different surfaces.

The SIMATIC MV320 handheld reader is suitable for wired communication. Due to the varied interface technology (USB, RS232), simple integration into your application is possible with the device.

The optical SIMATIC MV320 handheld reader is supplied as a package including USB cable. A separate package comprising cable and power supply is available for use as an RS232 version.

Design

The SIMATIC MV320 handheld reader features a robust, ergonomic handle with integrated strain relief.

The SIMATIC MV320 is a monolithic product and thus extremely robust. The only replaceable component is the cable that is connected to the reader with protected strain relief but can nevertheless be easily replaced for the purpose of changing the interface technology.

Integration

The SIMATIC MV320 handheld readers can communicate with the host computer by means of RS232 and USB. No special software is required for this purpose. The SIMATIC MV320 is configured by reading supplied data matrix codes.

The optical handheld reader can only be operated via RS232 and USB for direct transfer of the codes to the host computer. "Batch mode" is not possible.

Technical specifications	
Article number	6GF3320-0HT01
Product type designation	MV320 optical handheld reader
Suitability for operation	1D/2D: Aztec, Codabar, Codablock F, Code 11, Code 39, Code 39 Short Margin, Code 39 Extended Full ASCII, Code 39 Checksum, Code 93, Code 128, Code 128 Short Margin, Composite, Data Matrix, Data Matrix Rectangle, Data Matrix Inverse, GS1 DataBar (all), Interleaved 2of5, Interleaved 2of5 - 2 Digits, Macro PDF417, Maxicode, Matrix 2of5, Micro PDF417, MSI Plessy, NEC 2of5, OCR, PDF417, Postal Codes (All), QR Code, Telepen, UPC, UPC Short Margin, UPC Extension
Range	20 375 mm
Range Note	Range depends on the type and size of code. See manual for details
Optical data	
of the camera	image resolution 960 x 640
Mounting type of lens	Integrated
Type of light source	Lighting system comprising incident light (red)
Image acquisition frequency maximum	10 Hz
Type of focusing	Fixed focus, optimum focal point at 6.3 mm
Supply voltage, current	
Type of current supply	Via USB or external plug-type power supply unit (RS232), 5 V, 410 mA
Type of battery	
Permitted ambient conditions	
Ambient temperature	
 during operation 	-20 +55 °C
 during storage 	-30 +65 °C
Relative humidity at 25 °C without condensation during operation maximum	95 %
Height of fall maximum	1.8 m
Design, dimensions and weight	
Width	132 mm
Height	52 mm
Depth	92 mm
Net weight	0.13 kg
Product properties, functions, components general	
Design of the display	2 LEDs
Operator element version	Irigger in handle
Design of acoustic signaling element	Vibration alarm, audible signal
Design of the interface	USB, HS232
configuration	
Product function of the software	Read, display, save, transfer codes
Type of programming	Optical parameterization or via configuration software
Accessories	-
Accessories	RS232 cable with power supply, USB cable, metal stands

4/39

Handheld reading systems

SIMATIC MV320

Selection and ordering data		Dimensional drawings
	Article No.	
SIMATIC MV320	6GF3320-0HT01	
Rugged industrial handheld reader for barcodes and data matrix codes, with 1.8 m USB cable.		131.7
Accessories		
USB cable	6GF3320-0AC02	
1.8 m long, not spiraled		91.5
RS232 cable	6GF3320-0AC03	++
2.4 m long, spiraled		
		6. FS10.202_01148
		SIMATIC MV320 optical handheld reading device
Plug-in power supply		
For use with RS232 cable		
• For the USA	6GF3020-0AC40-0AP1	
For Europe	6GF3020-0AC40-0AP2	
Metal stands	6GF3320-0AC07	

SIMATIC MV325

Overview





The SIMATIC MV325 handheld reader is a robust, high-performance industrial barcode and data matrix code reader suitable for high resolutions. It reads two-dimensional (2D) data matrix codes and one-dimensional (1D) barcodes.

Medium to high contrast data matrix codes can be read. The cell size should be larger than 0.13 mm. Barcodes can be read if the width of a bar is larger than 0.12 mm.

The reader possesses complex image processing functions and illumination technology in order to read codes on many different surfaces.

The SIMATIC MV325 handheld reader is suitable for wireless communication. Thanks to Bluetooth interface technology, simple integration into your application is possible with the device.

The handheld reader is supplied as a package including a charging station and USB cable.

Design

The optical SIMATIC MV325 handheld reader has a replaceable battery pack and is extremely rugged. The only replaceable component is the battery that can be charged together with the reader or individually in the charging station.

Integration

The charging station of the SIMATIC MV325 can communicate with the host computer by means of USB. No special software is required for this purpose. The SIMATIC MV325 is configured by reading supplied data matrix codes.

The SIMATIC MV325 handheld reader itself communicates via Bluetooth with the base station. No special software is required for connecting a handheld reader with a specific charging station since the SIMATIC MV325 is connected with the charging station by reading a unique identifier on the charging station.

The code contents read are automatically transferred to the charging station as soon as a wireless connection is established. If the connection to the charging station is not established, the read results are buffered in the mobile section (if this function is activated). This operating mode is referred to as batch mode. As soon as the connection to the charging station is restored, the read results are automatically transferred.

Handheld reading systems

SIMATIC MV325

Technical specifications

Article number	6GF3325-0HT01
Product type designation	MV325 optical handheld reader
Suitability for operation	1D: Codabar, Code 11, Code 32, Code 39, Code 93, Code, 128, Interleaved 2 of 5, GS1 DataBar (RSS), Maxtrix 2of5, MSI Plessey, Plessey, Straight 2of5, Trioptic, UPC/EAN/JAN
	Stacked 1D: GS1 Composite (CC-A/CC-B/CC-C), MicroPDF, PDF417
	2D: Aztec Code, Data Matrix, Micro QR Code, QR Code, Han Xin
Range	20 375 mm
Range Note	Range depends on the type and size of code. See manual for details
Optical data	
Design of image sensor of the camera	CMOS 1 280 x 960, image resolution 960 x 640
Mounting type of lens	Integrated
Type of light source	Lighting system comprising incident light (red)
mage acquisition frequency maximum	10 Hz
Type of focusing	Fixed focus, optimum focal point at 6.3 mm
Supply voltage, current	
Type of current supply	Battery operation
Type of battery	Lithium ion accumulator
i)po oi balloi j	fast charging capability
Battery capacity	1.3 Ah
Operating period with standard bat-	12 h
Permitted ambient conditions	
Ambient temperature	
 during operation 	-20 +55 °C
 during storage 	-30 +65 °C
Relative humidity at 25 °C without condensation during operation maximum	95 %
Height of fall maximum	1.8 m
Design, dimensions and weight	
Width	135 mm
Height	51 mm
Depth	130 mm
Net weight	0.18 kg
components general	
Design of the display	6 LEDs
Operator element version	Trigger in handle
Design of acoustic signaling element	Vibration alarm, audible signal
Design of the interface	Bluetooth Class 2, USB
Product functions management, configuration	
Product function of the software	Read, display, save, transfer codes
Type of programming	Optical parameterization or via configuration software
Accessories	
Accessories	Changeable accumulator for 50000 readings (Lion 3.7 V / 1.3 Ah), external charging station (power supply via USB) incl. Bluetooth Accesspoint

Selection and ordering data

	Article No.
SIMATIC MV325	6GF3325-0HT01
Robust industrial optical handheld reader for 1D and 2D codes (e.g. barcodes and data matrix codes), with charging station and USB cable. With Bluetooth wireless interface and charging station with USB host interface.	
Accessories	
Charging station	6GF3325-0AC03
Charging station with USB host interface and with Bluetooth wireless interface. With USB cable (0.9 m).	
Battery	6GF3325-0AC07
Lithium ions (1300 mAh; 50 000 charging cycles)	
DU000	

Dimensional drawings



SIMATIC MV325 optical handheld reading device

Overview

USB



The SIMATIC MV340 is one of the most powerful handheld readers in the world and is thus particularly suitable for demanding applications. The reader reads a wide range of direct part markings (DPM), from linear barcodes all the way to 2D symbols. Different codes can be read without having to reconfigure the device.

50 mm

Light

The optical MV340 handheld reader is designed for close ranges and records codes at a distance of up to 50 mm. The optimum reading distance is 6 mm. The special integrated lighting is ideal for a wide variety of surfaces and increases the contrast with stamped codes. Low-contrast reading despite fluctuating lighting conditions and twisted or damaged codes are the strengths of the SIMATIC MV340.

The SIMATIC MV340 handheld reader is connected via a USB or RS232 interface to the IT system or HMI device.



Design

The SIMATIC MV340 is a fully integrated device that combines a powerful reader unit and lighting in a rugged housing with an ergonomically shaped handle. The read process is triggered by a switch on the handle. Feedback from the read process can be optical via a multi-color LED, acoustic, or by means of a vibrating alarm

The special integrated lighting unit can switch automatically between different lighting types to always provide optimal lighting conditions for a wide range of code and surface types. Even lowcontrast codes or dot peen markings are therefore no longer a problem.

The device is supplied with a USB cable as standard. An RS232 cable can be ordered separately as an accessory.

Integration

The SIMATIC MV340 is connected via USB or RS232. The free ESP software is available for user-friendly set-up of the device. As an alternative, the device can be installed and operated without special software since it can also be configured by reading supplied data matrix codes.

The power supply is solely via cable. If the device is connected via USB to the host computer, the supply voltage is applied directly via the USB port. Connection to the RF170C communication module is also via the USB port. If the connection is via RS232, an additional power supply unit is required which is coupled to the RS232 connector via Y-cable. The power supply unit is available in three variants: EU, UK, and USA.

Handheld reading systems

SIMATIC MV340

Technical s	pecifications
-------------	---------------

Article number	6GF3340-0HT01
Product type designation	MV340 optical handheld reader
Suitability for operation	1D Codes: Int. 2/5, Code 128, Code 93, Code 39, EAN/UPC, Codabar, BC 412
	2D-Codes: DMC, PDF417, QR, GS1 Databar
Range	0 50 mm
Range Note	Code-dependent
Optical data	
Design of image sensor of the camera	CMOS 1 280 x 1 024
Mounting type of lens	Integrated
Type of light source	Lighting system comprising diffuse incident light (light field: red/blue) and dark field (red)
Image acquisition frequency maximum	10 Hz
Type of focusing	Fixed focus, optimum focal point at 6.3 mm
Supply voltage, current	
consumption, power loss	
Type of current supply	supply unit (RS232), 5 V, 410 mA
Type of battery	
Permitted ambient conditions	
Ambient temperature	
during operation	0 50 °C
during storage	-20 +65 °C
condensation during operation maxi- mum	95 %
Height of fall maximum	1.8 m
Design, dimensions and weight	
Width	180 mm
Height	63 mm
Depth	114 mm
Net weight	0.2 kg
Product properties, functions, components general	
Design of the display	Multi-color LED
Operator element version	Trigger in handle
Design of acoustic signaling element	Vibration alarm, audible signal
Design of the interface	USB, RS232
Product functions management, configuration	
Product function of the software	Read, display, save, transfer codes
Type of programming	Optical parameterization or via configuration software
Accessories	3
Accessories	RS232 cable with power supply

Selection and ordering data

	Article No.
SIMATIC MV340	6GF3340-0HT01
Robust industrial optical reader for barcodes and data matrix codes, with special integrated lighting. Suitable for demanding, i.e. low- contrast, marking systems. With USB cable.	
Accessories	
RS232 cable	
 2.4 m long, spiraled. 	6GF3020-0AC40-0AC1
 2.4 m long, spiraled, with power supply for USA. 	6GF3020-0AC40-0AC3
 2.4 m long, spiraled, with power supply for Europe. 	6GF3020-0AC40-0AC4
 2.4 m long, spiraled, with power supply for UK. 	6GF3020-0AC40-0AC5
 5 m long, spiraled. 	6GF3020-0AC40-0AC7
 5 m long, spiraled, with power supply for Europe. 	6GF3020-0AC40-0AC8
USB cable	6GF3020-0AC40-0AC0
1.8 m long, not spiraled.	
Power supplies	
For use with RS232 cable	
• For USA.	6GF3020-0AC40-0AP1
• For Europe.	6GF3020-0AC40-0AP2

Dimensional drawings



SIMATIC MV340 optical handheld reading device

Verification systems

Overview



Marking a product is normally done very early on in the production process so that all following steps can be controlled using the product identity.

By using verification systems, the readability of marks is guaranteed throughout the entire production process regardless of any possible contamination or when using different read devices. Moreover, the marking can continue to be read after the production process throughout the lifespan of the product.

With the verification license "Veri-Genius", devices of the SIMATIC MV440 family can be used for checking the marking quality of codes (verification) in addition to reading 1D barcodes and 2D matrix codes.

The license is supplied as a "Single License" on a USB flash drive and can be installed via the SIMATIC Automation License Manager (ALM) on any reader of the SIMATIC MV440 series. The license is executable on a SIMATIC MV440 as of firmware version 4.0.

Benefits

Designed for Industry get

Support for all important sectors and code types through the following verification standards:

- ISO TR 29158 (previously AIM DPM-1-2006)
 - Code type: Data Matrix Code
 - Type of marking: All focus on DPM,
 - e.g. dot-peened and lasered markings
 - Industries: All focus on DPM,
 - e.g. dot-peened and lasered markings
- Siemens DPM
 - Code type: Data Matrix Code
 - Type of marking: All focus on DPM, e.g. dot-peened and lasered markings
 - Industries: All
- ISO/IEC 15415
 - Code type: Data Matrix Code
 - Type of marking: Printed
 - Sectors: All focus: Pharmaceutical industry
- AS9132 Rev. A (previously IAQG)
- Code type: Data Matrix Code
- Type of marking: Printed
- Sectors: All focus: Aerospace
- ISO/IEC 15416 (previously ANSI X3.182-1990)
 - Code type: Barcode
 - Type of marking: Printed
 - Sectors: All printed labels

Further highlights

- Various resolutions available
- (640 x 480 pixels, 1 024 x 768 pixels and 1 600 x 1 200 pixels)
- License includes calibration card
- Simultaneous reading and verifying in one field of view
- Flexible retrofitting of the license to each device of the SIMATIC MV440 series via the Automation License Manager of SIMATIC – advantage: Savings with stocking spare parts
- Easy integration of verification into the automation environment via SIMATIC MV440 using a function block (FB 79, FB 45 and Ident profile).

Verification systems

Veri-Genius for MV440

Application

Applications for verification span across almost all sectors. To maximize read rates in production and logistics and to make them predictable, it is essential to measure the marking quality.

The following sectors and applications are a particular focus for MV440 verification systems:

Automotive industry

- Needle marking (DPM):
- e.g. cylinder heads, cylinder blocks, etc.Laser marking (DPM):
- Cylinder pistons, gearbox components, etc.Laser markings on electronic components,
- printed circuit boards, or enclosures

Pharmaceutical industry

- Print or laser markings on medicines (DPM, OCR)
- · Aerospace industry
- Needle or laser markings on gas turbine blades (DPM)
- Needle or laser markings on jet engine components (DPM)

Medical equipment

- Laser markings on implants (DPM)
- Laser markings on medical devices (DPM).

Electronics

- · Needle or laser markings on hard disk components.
- Laser or etched markings on hard disk components (DPM)

Semiconductors

- Laser markings on rigid and flexible circuit boards (DPM)
- Laser markings on enclosed semiconductor components, heat sinks or heat exchangers (DPM)

"Veri-Genius" can be used anywhere where ambient conditions permit the use of the MV440 optical reader - for details, see SIMATIC MV440. Standard ring lights and lenses are designed to achieve IP67 degree of protection by means of the protective barrel, and for glass-free use in the food and beverages industry. If light sources or lenses are used outside the protective barrel, they must be used in compliance with their specification.

Any host and HMI systems required must be selected for a sector and a specific project. The range of application of the selected test method is defined in the specification of the test method and compliance is essential if universally valid results are to be obtained.

Design

All stationary optical SIMATIC MV440 readers are basic units under the terms of the "Veri-Genius" license. The verification functionality is enabled by transferring the license key from the supplied USB flash drive to the optical MV440 reader by means of SIMATIC License Manager.

The functionality is available without a license in demo mode. The functions subject to licensing are fully available without performance restrictions in Demo mode. Only output of the results on the communication channels is disrupted. Users can therefore determine in Demo mode if the functions and performance fulfill their requirements.

Verification with MV440 verification systems is suitable for both inline and offline measurements. In both cases, the specification of the verification standard used must be observed to ensure a robust measurement result. This means that, for example, the lighting and alignment of the light source, camera and test object must be selected in accordance with the specifications of the respective standard.

If only one light source is used, the MV440 can control an external light source using the existing image-synchronized digital output, or the external light source can be operated continuously.

If more lighting directions are required, an external controller can be used to activated the desired lighting and to start each individual measurement by means of triggering. The result from the quality measurement or the relevant partial measurement is output directly by the MV440 after completion of the measurement. In the case of more than one measurement, it is the task of the external controller to combine the partial results into an overall result and to visualization this.

For a measurement with only one type of lighting, the measurement result can be visualized directly as a verification report in the form of an HTML page which can then be printed out.

If the test method requires calibration, the calibration card included in the scope of delivery can be used in most cases. In cases with extreme imaging requirements (e.g. with very small or very large codes), the task of calibration must be resolved application-specifically.

Verification systems

Veri-Genius for MV440

Function

The following typical types of fault can be detected by measuring the marking quality - the following pictures show examples of correct code and faults in the marking quality:



Correct code



Incorrect or non-uniform cell size in the marking



Incorrect or non-uniform cell size in the marking



Incorrect or non-uniform cell position in the marking



Incorrect overall geometry of the marking



Damaged surface of the marking or part



Very little or non-uniform contrast in the marking



Very little or non-uniform contrast in the marking

The following measuring procedures/standards are available for the purposes of inspection:

- ISO TR 29158 (previously AIM DPM-1-2006)
- Siemens DPM
- ISO/IEC 15415
- AS9132 Rev. A (previously IAQG)
- ISO/IEC 15416 (previously ANSI X3.182-1990)

Siemens ID 10 · 2016

4

Verification systems

Veri-Genius for MV440

The measurement result is output as an overall result in 5 stages, which are named using letters or numbers:

Overall result as a digit	Overall result as letters	Overall result as text
4	A	Top quality
3	В	Good quality
2	C	Satisfactory quality
1	D	Adequate quality
	E	(not used)
0	Fault	Marking quality inadequate

The components of a measurement result and calculation of the overall result are dependent on the test method used.

The overall result and the components of a measurement result can be output after a test, and are then available for further processing on an external system, e.g. for archiving or creating a test report.

Veri-Genius for MV440

Integration

The MV440 verification systems can use all communication services that the SIMATIC MV440 basic unit offers:

Usable communication services	
PROFINET IO (FB 79)	Onboard MV440 PROFINET interface.
PROFINET IO (FB 101, Ident profile)	Onboard MV440 PROFINET interface.
PROFINET IO (FB 45, FB 101, Ident profile)	Via MV440 communication module interface, using the RF180C communication module.
Ethernet/IP	Via communication module interface, with communication module RFID 181EIP.
PROFIBUS DP V0/1 (FB 45, Ident profile)	Via MV440 communication module interface, using the ASM 456 communication module.
TCP/IP native	Onboard MV440 PROFINET interface.
RS232 (ASCII)	Onboard MV440 RS232 interface.
SIMATIC S7-1200, S7-300, ET 200pro	Via communication module interface.

The most important types of interface in the automation environment are shown in the overview below.

Refer to the section on the SIMATIC MV440 for additional details.



Selection and ordering data

	Article No.
Verification module Veri-Genius	6GF3400-0SL02
Software license for verification of machine- readable 1D barcodes and Data Matrix Codes.	
The license is supplied on a USB flash drive; executable on all optical SIMATIC MV440 readers as of firmware V4.0 (SIMATIC MV440 not included in the scope of delivery).	
The scope of supply includes the calibration card.	
Calibration card	6GF3440-8CE
Spare part	

Optical character recognition (OCR)

Text-Genius for MV440

Overview



With the "Text-Genius" and "Text-Genius Plus" licenses, SIMATIC MV440 can be used for text recognition (in addition to reading 1D barcodes and 2D matrix codes).

Text recognition is also referred to as OCR (Optical Character Recognition). Simultaneous reading and comparing of plain text and reading of machine-readable codes in the same field of view is thus possible.

"Text-Genius" allows text recognition without training for a number of character sets by using generic algorithms, and thus reading without a preparatory phase.

SIEMENS	SIMATIC M	V440 UR	OC	R+			WE	E
						Ľ	Deutsch	•
Kentwort *** Abmelden Anmelden	Programme Nummer: 1	2.881					Bibliothe	ka
Einrichten Verbindungen	Zeichenfonts F1	F2 8 8	Erzeugen	Zuordner	n Spei	chern		
Ausweiten > Optionen > Into > Verwaten > Stopp > Startsene	Ansicht: Kategorie: A A 4 5 7 K 2 Exchen: 0 - 2 2 Cualdat 0 - 255 Birelet: 5 - 55 Holne: 15 - 65 Arcant.	000 1112 335 888 900 FLU	10000 11111 22223 55556 56666 88999 166666	013969F		1111 5566 8389	16.	
ETHERNET STATE/SF	Suchen	Zuordnen:	1 <u>A X</u>	Zu	ordnung ändern:	<u> </u>	D×	
								N

© Siemens AG 2012. Alle Rechte vorbehaten

Text-Genius Plus

The "Text-Genius Plus" license comprises all functions of the "Text-Genius" license and additionally enables training of further fonts and characters, including special characters and graphic symbols.

Licenses

The licenses are supplied as a "Single License" on a USB flash drive and can be copied to the device with the SIMATIC Automation License Manager (ALM) using a plug-in. The "Text-Genius" license is executable on a SIMATIC MV440 with firmware version 3.0 and higher, the "Text-Genius Plus" license with Firmware version 5.0 and higher.

Benefits



Highlights of Text-Genius and Text-Genius Plus at a glance

- Quick and reliable reading (up to than 2000 readings per minute depending on the application) for high-speed applications.
- Fast and reliable checking of the readability of plain text (up to 1 000 reads per minute) for high-speed applications.
- Flexible reading and swapping between different fonts (e.g. OCR A, OCR B) without complex learning using Polyfont character set.
- High reading rate and reliability through saving of fonts on the camera.
- Reading and comparison of plain text and machine-readable code in the same image field.
- Automatic position tracking of the reading range with the resources of "Pat-Genius".
- Automatic text localization without the use of predefined areas means that text can be read even when its position varies.
- Automatic line detection for max. 12 freely definable image regions with max. 15 lines.
- Automatic character height recognition between 15 and 220 pixels.
- Individual parameterization per image region.
- Reading of mirrored, 90° rotated, and inverted text.
- Numerous filter and comparison functions.
- Comparison of text recognition result with an individually specified text per read operation.
- Flexible retrofitting of the text recognition function via the SIMATIC Automation License Manager
- Simple integration in the automation environment, e.g. via function block of the SIMATIC MV440 devices.

Additional highlights of Text-Genius Plus:

- Simple training of additional characters and fonts (user fonts).
- Adaptation of text recognition by user fonts to the specific requirements of the application to enable:
 - Expansion of defined fonts by missing characters, e.g. special characters.
 - Optimization of recognition for specific printing procedures (e.g. laser, ink, scribed, needled).
 - Optimization of recognition by using different versions of individual characters, e.g. to compensate distortions.
- Up to five user fonts can be used in the reader.
- Very high read reliability can be achieved (> 99.5%).

Optical identification Optical character recognition (OCR)

Text-Genius for MV440

Application

Applications for text recognition span across almost all sectors. The application areas can be generally divided in three task areas:

- Text recognition for recording the content of a plain text identification.
- Comparison of the content of a plain text identification with the content of the adjacent machine-readable identification, e.g. Data Matrix Code (DMC).
- Comparison of the content of a plain text identification with individually specified values which are transferred to the reader similar to a printer.

Applications for different sectors are listed below. The list is incomplete and only serves to illustrate the wide range of possible applications.

Automotive industry, aerospace industry

- Detection and checking of plain text identifiers for type identification of components
- · Comparison of DMC and plain text
- Acquisition of a unique identification of a product (serialization)
- · Acquisition and checking the expiry date

Medical equipment

- Laser markings on implants (DPM)
- · Laser markings on medical devices (DPM).

Electronics

- Detection of a unique plain text identifier for identifying devices, e.g. electricity meters
- Detection and checking of plain text identifiers for type identification of PCBs
- Solar industry (serial numbers on thin-layer modules)
- Detection of a unique plain text identifier on thin-layer modules (serialization)

Food and beverage industry

- Inspection of expiry date on packaging
- · Control of packaging and storage processes

"Text-Genius" and "Text-Genius Plus" can be used anywhere where ambient conditions permit the use of the optical reader SIMATIC MV440. For details, see "SIMATIC MV440". Standard ring lights and lenses are designed to achieve IP67 degree of protection by means of the protective barrel, and for glass-free use in the food and beverages industry. If light sources or lenses are used outside the protective barrel, they must be used in compliance with their specification.

The "text recognition" function can be implemented in applications without the need to consider the type of font used for marking (Polyfont) or the marking method. The fonts which enable a maximum read rate to be achieved are listed in the "Function" chapter. Further fonts and additional characters can be added to Text-Genius Plus at any time by training. No marking methods are excluded either. The read rate improves if the font has a stable appearance and when there is a good contrast between the background and marking.

Design

All stationary optical SIMATIC MV440 readers are basic units under the terms of the "Text-Genius" and "Text-Genius Plus" licenses. The text recognition functionality is enabled by transferring the license key from the supplied USB flash drive to the MV440 reader by means of SIMATIC License Manager.

The functionality is available without a license in demo mode. The functions subject to licensing are fully available without performance restrictions in Demo mode. Only output of the results on the communication channels is disrupted. Users can therefore determine in Demo mode if the functions and performance fulfill their requirements.

Function

The outstanding feature of "Text-Genius" and "Text-Genius Plus" is that they are easy to set up. To achieve stable read results for text recognition, it is only necessary to set a few, simple parameters. "Text-Genius" uses a generic approach for text recognition, so no individual training is required for most fonts and the characters (letters and digits) of the ASCII character set. Recognition of several fonts is thus possible with this software without specific training. In particular, no complex settings are required for optimizing recognition performance.

The following fonts are ideal for recognition of the text:

- OCR-A
- Semifont M13
- and similar fonts

Furthermore, Arial, OCR-B and similar fonts also produce good reading results.

"Text-Genius Plus" additionally allows the training of additional characters for any character set. Expansion of the character set is required to allow recognition of characters which are not included or of those which are deformed as a result of the printing process.

The character sets of the "Text-Genius" license are available as the basis for text recognition with "Text-Genius Plus", meaning that text recognition can be started immediately without further training. "Text-Genius Plus" is particularly suitable for applications with a varying print image and unknown fonts.

Optical character recognition (OCR)

Text-Genius for MV440

Integration

The MV440 text recognition systems can use all communication services that the SIMATIC MV440 basic unit offers:

Usable communication services	
PROFINET IO (FB 79)	Onboard MV440 PROFINET interface.
PROFINET IO (FB 101, Ident profile)	Onboard MV440 PROFINET interface.
PROFINET IO (FB 45, FB 101, Ident profile)	Via MV440 communication module interface, using the RF180C communication module.
Ethernet/IP	Via communication module interface, with communication module RFID 181EIP.
PROFIBUS DP V0/1 (FB 45, Ident profile)	Via MV440 communication module interface, using the ASM 456 communication module.
TCP/IP native	Onboard MV440 PROFINET interface.
RS232 (ASCII)	Onboard MV440 RS232 interface.
SIMATIC S7-1200, S7-300, ET 200pro	Via communication module interface.

The most important types of interface in the automation environment are shown in the overview below.

For further details, refer to the chapter on SIMATIC MV440.



Optical identification Optical character recognition (OCR)

Text-Genius for MV440

Selection and ordering data

	Article No.
OCR module Text-Genius	6GF3400-0SL01
Software license for reading machine-readable 1D barcodes and 2 D matrix codes, as well as for optical character recognition.	
The license is supplied on a USB flash drive; executable on optical SIMATIC MV440 readers as of firmware V3.0 (SIMATIC MV440 not included in the scope of delivery).	
OCR module Text-Genius Plus	6GF3400-1SL01
Software license for machine- readable text recognition (OCR) and for reading 1D barcodes and 2 D matrix codes. Trainable text recogni- tion allows the training of individual characters or even complete charac- ter sets. The character sets of Text- Genius are provided as trained, expandable libraries.	
The license is supplied on a USB flash drive; executable on optical SIMATIC MV440 readers as of firmware V5.0 (SIMATIC MV440 not included in the scope of delivery).	

Object recognition

Overview



Objekterkennung mit Pat-Genius

With the object recognition license "Pat-Genius", devices of the SIMATIC MV440 family can also be used for checking the specifiable structures in the image (verification) in addition to reading 1D barcodes and 2D matrix codes.

The license is supplied as a "Single License" on a USB flash drive and can be installed via the SIMATIC Automation License Manager (ALM) on any reader of the SIMATIC MV440 series. The license can be installed on a SIMATIC MV440 as of firmware version 6.0.

Benefits

get Designed for Industry

- Pat-Genius shape recognition contains the following different partial tasks:
 - Object recognition (classification)
 - Position detection (position, rotational position, scaling)
 - Presence check (object recognition and position check with setpoint specification)
 - Completeness check (multiple presence check with setpoint specification)
 - Text recognition (based on the contour of any character or symbol)
- Pat-Genius is easy to operate thanks to its integration in the uniform operating concept for all function packages in the user interface of the MV440 devices
- Pat-Genius can be used together with all other function packages (Text-Genius and Veri-Genius) of the SIMATIC MV440 devices.
- Pat-Genius is available for all resolution versions of the SIMATIC MV440 (640 x 480 pixels, 1 024 x 768 pixels and 1 600 x 1 200 pixels).
- Pat-Genius can be flexibly retrofitted for every device of the SIMATIC MV440 family (via the SIMATIC Automation License Manager). Customer benefit: Cost benefits with stocking spare parts.
- Pat-Genius licenses are transferrable between all SIMATIC MV440 devices without regard for the resolution capacity.
- Pat-Genius supports the proved simple integration of the SIMATIC MV440 devices into the automation environment using a function block (FB 79, FB 45 and FB 101) for the SIMATIC S7-1200, S7-1500, S7-300 and S7-400 controllers.

Object recognition

Pat-Genius for MV440

Application

The functionality of object recognition is basically suitable for applications such as

- Pick-and-place machines
- Quality control in production
- · Position detection in infeed systems
- · Quantity monitoring in infeed systems and production

Pat-Genius can be used anywhere where ambient conditions permit the use of the optical MV440 reader - for details, see SIMATIC MV440. Standard ring lights and lenses are available for IP67 degree of protection by means of the protective barrel, and for glass-free use in the food and beverages industry. If light sources or lenses are used outside the protective barrel, they must be used in compliance with their specification.

Any host and HMI systems required must be selected for a sector and a specific project. The range of application of the selected test method is defined in the specification of the test method and compliance is essential if universally valid results are to be obtained.

The following sectors and applications are a particular focus for MV440 verification systems:

Automotive industry

For example:

- Testing the manufacturing process: e.g. assembling the body in white, etc.
- Access control for semi-finished products for machining stations in the process: Cylinder heads, etc.
- Monitoring the uniformity of the assembly quality in the manufacturing process

Pharmaceutical industry

For example:

- Checking of warning information on medicines (e.g. Caution poisonous)
- Checking of the correct arrangement of the content and the closing mechanism in the packaging process
- · Checking the filling level of packages

Medical equipment

For example:

 Inline quality check and documentation by means of checking completeness and shape consistency

Electronics

For example:

• Inline quality check and documentation by means of checking completeness and shape consistency

Semiconductors

For example:

- · Detecting the alignment of components
- · Controlling the dimensional accuracy of components

Design

All SIMATIC MV440 stationary optical code reader are basic units under the terms of the "Object recognition" functionality, which is subject to license. The text recognition functionality is enabled by transferring the license key from the supplied USB flash drive to the MV440 reader by means of SIMATIC License Manager.

The functionality is available without a license in demo mode. This function subject to licensing is fully available without performance restrictions in Demo mode. Only output of the results on the communication channels is disrupted. Users can therefore determine in Demo mode whether the functions and performance fulfill their requirements.

Function

The object recognition detects deviations in the current camera image relative to a learned structure using edge structures.

Accordingly, the basic test sequence is as follows:

- Training the object test parameters using one or more good objects
- Testing an object and/or pattern with the features taken from the training
- Testing can be performed on stationary and moving objects
- Checking for a match with the reference provides a good/poor indication after comparison with set-value criteria
- Test results output to three control outputs:
- OK: Presence of the trained objects and/or pattern recognized by characteristics
- OK: Level of agreement greater than setpoint
- ...
- N_OK: NO presence of trained objects with the specified characteristics
- N_OK: Deviation from degree of conformity to setpoint

- ...

- Output of the result information onboard via PROFINET IO, Ethernet, RS232 interface – further interfaces are available via communication modules
- "Stand-alone" mode possible using integrated DI/O
- Remote control via PROFIBUS IO, PROFINET DP (via communication module), DI/O or Ethernet
- Platform-independent, web-based interface (Internet-enabled):
 - Monitoring (live image in read mode)
 - Diagnostics (fault image, log information, ...)
 - System administration (software update, ...)
 - Error analysis for troubleshooting for faulty readings
- Triggering of external ring lights

The overall result and the components of a measurement result can be output after a test via different interfaces, and are then available for further processing on an external system, e.g. for archiving or creating a test report.

Object recognition

Pat-Genius for MV440

Integration

Pat-Genius for SIMATIC MV440 can use all communication services that the SIMATIC MV440 basic unit offers:

Usable communication services	
PROFINET IO (FB 79)	Onboard MV440 PROFINET interface.
PROFINET IO (FB 101, Ident profile)	Onboard MV440 PROFINET interface.
PROFINET IO (FB 45, FB 101, Ident profile)	Via MV440 communication module interface, using the RF180C communication module.
Ethernet/IP	Via communication module interface, with communication module RFID 181EIP.
PROFIBUS DP V0/1 (FB 45, Ident profile)	Via MV440 communication module interface, using the ASM 456 communication module.
TCP/IP native	Onboard MV440 PROFINET interface.
RS232 (ASCII)	Onboard MV440 RS232 interface.
SIMATIC S7-1200, S7-300, ET 200pro	Via communication module interface.

The most important types of interface in the automation environment are shown in the overview below.

For further details, refer to the chapter on SIMATIC MV440.



Selection and ordering data

	Article No.
IMATIC "Pat-Genius" license	6GF3400-0SL03
Software license for object recognition in image information on products of the SIMATIC MV440 family.	
The license is supplied on a USB flash drive; usable on all optical SIMATIC MV440 readers as of firmware V6.0 (SIMATIC MV440 not included in the scope of delivery).	

© Siemens AG 2016

Communication modules, RFID standard cables, SCALANCE network components





5/2	Communication modules for RFID systems and optical identification
5/4	ASM 456, RF160C
5/9	RF180C, RF182C, RFID 181EIP
5/16	RF170C
5/19	RF120C
5/22	ASM 475
5/25	RFID standard cables
5 /25 5 /27 5/28	RFID standard cables SCALANCE network components Industrial Ethernet switches SCALANCE X

Introduction

Overview



5

SIMATIC Ident integration graphics

There are various powerful communication modules (ASM) for integrating SIMATIC RFID, SIMATIC MV and MOBY identification systems in SIMATIC, SINUMERIK, SIMOTION, PROFIBUS, PROFINET and Ethernet/IP.

Introduction

Selection aid for communication modules and software

System	Communication modules without file handler	Identification system	Available software
SIMATIC S7-1200	RF120C	RF200, RF300, RF600, MV400, MOBY D	Ident-Library (Read, Write, Reset_Reader etc.)
SIMATIC S7-300 (direct), S7-300/400, PC with SIMATIC WinAC via ET 200M, SINUMERIK 840D/810D	ASM 475	RF200, RF300, RF600, MV400, MOBY D	FB 45, FB 55
Serial link, to PC, PLC or any other system ¹⁾	Direct via SLG Dx	MOBY D	MOBY D MDWAPI,
	Direct via RF2xxR, RF3xxR (RS422 / RS232) reader	RF200, RF300	C library incl. drivers for Windows XP/7
PROFIBUS DP (SIMATIC S7, PC, any other system ¹⁾)	RF160C	RF200, RF300, RF600, MOBY D	FC 44 for S7-300/400, PC with SIMATIC WinAC
SIMATIC S7, PC with SIMATIC WinAC, via ET 200pro	RF170C	RF200, RF300, RF600, MV400, MOBY D	FB 45, FB 55 (S7-300/400 only), Ident profile, Ident Library (for all S7; Read, Write, Reset_Reader etc.)
PROFIBUS DP-V1 (SIMATIC S7, SIMOTION SCOUT, PC, any other system ¹⁾)	ASM 456	RF200, RF300, RF600, MV400, MOBY D	FB 45, FB 55 (S7-300/400 only), FB101/116/132, Ident profile, Ident Library (for all S7; Read, Write, Reset_Reader etc.)
PROFINET IO	RF180C	RF200, RF300, RF600, MV400, MOBY D	FB 45, FB 55 (S7-300/400 only), FB 101/116/132, Ident profile, Ident Library (for all S7; Read, Write, Reset_Reader etc.)
Ethernet TCP/IP	RF182C	RF200, RF300, RF600, MOBY D	XML application examples
Ethernet/IP	RFID 181EIP	RF200, RF300, RF600, MV400, MOBY D	Programming via implicit/explicit messages

System	Communication modules without file handler	Identification system	Available software
SIMATIC S7, PC, any other system, SIMOTION SCOUT	ASM 456	RF300	FC 56, FB 101/116/132
Ethernet/IP	RFID 181EIP	RF300	Programming via implicit/ explicit messages

Function

Corresponding software blocks (FB, FC, libraries, examples) ensure simple and quick integration into the application.

1 or 2 readers can be connected to a communication module (CM, ASM) with a maximum cable length of 1 000 m (depending on the CM, ASM, reader, etc.). Corresponding procedures guarantee a very high reliability of data transmission.

For the serial connection of SIMATIC RFID to any system (PC, PLC, etc.) the readers can be directly connected via an RS232 port.

Note regarding FC 45/55

The FC 45/55 can still be used in existing applications. For new applications, however, the FB 45/55 blocks or the Ident profile are recommended because only these blocks contain all functions.

Integration

SIMATIC Ident Configuration Guide

Here is a compact configuration tool for setting up RFID systems:n:

http://support.automation.siemens.com/WW/view/en/67384964

Notes regarding software and licensing

No software or documentation is supplied when purchasing a communication module (CM) or reader, The DVD "RFID Systems Software & Documentation" contains all the FBs/FCs available for SIMATIC, C libraries for Windows XP/7 operating systems, demo programs, etc. and must be ordered separately. In addition, the DVD contains the complete RFID documentation in all available languages in PDF format.

The purchase of a CM or reader includes a payment for use of the software, including documentation, on the DVD "RFID Systems Software & Documentation". The purchaser acquires the right to make copies (copy license), insofar as they are required as part of the plant project.

The General License Conditions, included on the respective DVD, shall apply.

ASM 456, SIMATIC RF160C

Overview



PROFI BUS

The low-cost communications modules ASM 456 and SIMATIC RF160C are stand-alone PROFIBUS DP slaves for the operation of MOBY D, SIMATIC RF200 / RF300 / RF600 RFID systems as well as the MV400 optical reader devices via PROFIBUS DP on:

- SIMATIC S7 (including FB/FC software)
- SINUMERIK
- PC, IPC, non-Siemens PLC
- SIMOTION (with integrated software library)

Thanks to their high degree of protection and ruggedness, they are particularly suitable for machine-level use. The modular structure with different PROFIBUS connection systems allows them to be used in all applications. The uniform plug-in connection system ensures rapid commissioning.

Benefits



- Two parallel MOBY channels ensure real-time mode at dynamic read points.
- Modular design with different bus interfacing possibilities ensures universal implementation.
- Reader connection using an 8-pin M12 connector for quick mounting of all components.
- High-performance hardware ensures fast data exchange with the reader. Consequently, data is available for the application even faster.
- Simple firmware downloading via the TIA Portal in the case of function expansions and error rectification ensures high availability of the identification system.
- The parameterizable identification-system-specific PROFIBUS diagnostics facilitate start-up and troubleshooting.
- A wide selection of pre-assembled PROFIBUS connecting cables can be ordered for the communication modules. This saves time and money during installation and assures better quality.

Application

The ASM 456 and SIMATIC RF160C communication modules have been specifically designed for a wide range of applications in industrial automation and logistics. Thanks to the high IP67 degree of protection, the ASM 456 and RF160C can be installed in the process without a control cabinet.

Main application areas for ASM 456 and RF160C:

- Mechanical engineering, automation systems, conveyor systems
- Ancillary assembly lines in the automobile industry/suppliers
- Small assembly lines
- Production, packaging, textile, plastics and printing machines SIMOTION

Design



Configuration of ASM 456 and SIMATIC RF160C

Function

The ASM 456 and the RF160C comprise a basic module and a connection block that must be ordered separately. When connecting PROFIBUS, the customer can choose between ECOFAST connections and M12, 7/8" connections.

A pre-assembled reader cable, available in lengths from 2 m to 50 m, is used to connect one or two readers/SLGs to the communication module. The cable can also be assembled by the customer as required.

The PROFIBUS DP procedure according to EN 50170 Vol. 2 PROFIBUS for communication between the communication module and SIMATIC S7 (or any PROFIBUS master) and the MOBY-specific procedures for communication between ASM and reader are implemented on the communication modules.

The data in the transponder can be accessed as follows:

- · Direct addressing via absolute addresses
- Conveniently via the MOBY file handler (RF300 only) using file names (for ASM 456 only)

On the PROFIBUS DP, the communication module occupies a node address on the bus that is set on the connection block. The communication module is integrated into the hardware configuration by means of a device master (GSD) file. Then the communication module can be configured by means of the software tool HW_Config of the SIMATIC Manager or another PROFIBUS tool.

Error messages and operating states (transponder in the field, transmission active, etc.) are indicated additionally by means of LEDs and simplify commissioning and service.

ASM 456 and RF160C have two reader interfaces which also provide the readers with power. In the communication module, the power supply of the readers has an electronic fuse. If the reader requires more than 400 mA current (e.g. RF290R), only one reader can be operated on the communication module to avoid exceeding the maximum permissible current.

ASM 456

The ASM directly accesses the data in the transponder or the data matrix code via absolute addresses (FB/FC 45, FB/FC 55) or more conveniently using the MOBY file handler (FC 56) and file names. The communication module is operated in non-cyclic mode over PROFIBUS DP V1. Consequently, a very large amount of data can be transferred to/from the communication module without overloading the PROFIBUS cycle. This has advantages when transferring large volumes of data. In addition, the communication module can process concatenated transponder commands very quickly in this mode.

Function blocks FB 101/116/132 or the Ident Library in the SIMATIC S7 are available for the "RFID standard profile" mode. The Ident Library is integrated in the TIA Portal an doffers functions that are very easy to parameterize. The communication module is also integrated in SIMOTION by means of the "RFID standard profile" mode.

SIMATIC RF160C

The data in the transponder is accessed via absolute addresses. The FC 44 function block is available for SIMATIC S7 for this purpose. The RF160C is operated in cyclic mode over PROFIBUS DP-V0. This ensures a deterministic response in data communication in every case. Where there are large volumes of data, together with large-scale bus configurations, the data throughput should be tested with a tool which is provided on the DVD "RFID Systems, Software and Documentation". The programming interface to RF160C is extremely easy to use and can be programmed efficiently in any controller. The RF160C is therefore particularly suitable for use with non-Siemens controllers and older PROFIBUS masters.

Article number	6GT2002-0ED00	6GT2002-0EF00
Product type designation	ASM 456 communication module	RF160C communication module
Suitability for operation	PROFIBUS network according to DP-V1 together with RF200/300/600, MV400, MOBY D/E/I/U	PROFIBUS network according to DP-V0 together with RF200/300/600, MOBY D/U
Transmission rate		
Transfer rate with PROFIBUS	9.6 kbit/s 12 Mbit/s	9.6 kbit/s 12 Mbit/s
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	115.2 kbit/s
Interfaces		
Design of the interface for point-to-point connection	R\$422	RS422
Number of readers connectable	2	2
Type of electrical connection		
 of the PROFIBUS interface 	(according to the connection block)	(according to the connection block)
 for supply voltage 	(according to the connection block)	(according to the connection block)
Design of the interface to the reader for communication	M12, 8-pin	M12, 8-pin
Mechanical data		
Material	Thermoplastic (Valox 467, fiberglass reinforced)	Thermoplastic (Valox 467, fiberglass reinforced)
Color	IP Basic 714	IP Basic 714
Tightening torque of the screw for securing the equipment maximum	3 Nm	3 Nm

ASM 456	SIMATIC	C RF160C
	, on a	

Article number	6GT2002-0ED00	6GT2002-0EF00	
Product type designation	ASM 456 communication module	RF160C communication module	
Supply voltage, current consumption, power loss			
Supply voltage			
 at DC Rated value 	24 V	24 V	
• at DC	20 30 V	20 30 V	
Consumed current at DC at 24 V			
 without connected devices typical 	0.08 A	0.08 A	
 with connected devices maximum 	0.85 A	0.85 A	
Permitted ambient conditions			
Ambient temperature			
 during operation 	0 55 °C	0 55 °C	
 during storage 	-40 +70 °C	-40 +70 °C	
 during transport 	-40 +70 °C	-40 +70 °C	
Protection class IP	IP67	IP67	
Shock resistance	According to IEC 61131-2	According to IEC 61131-2	
Shock acceleration	300 m/s ²	300 m/s ²	
Vibrational acceleration	100 m/s ²	100 m/s ²	
Design, dimensions and weight			
Width	60 mm	60 mm	
Height	30 mm	30 mm	
Depth	210 mm	210 mm	
Net weight	0.21 kg	0.21 kg	
Mounting type	2 x M5 screws	2 x M5 screws	
Cable length for RS422	1 000 m	1 000 m	
Interface maximum			
components general			
Display version	4 LEDs per reader connection, 4 LEDs for device status	4 LEDs per reader connection, 4 LEDs for device status	
Product function transponder file handler can be addressed	Yes	No	
Protocol is supported			
 PROFIBUS DP-V0 protocol 	No	Yes	
 PROFIBUS DP-V1 protocol 	Yes	No	
Type of parameterization	GSD	GSD	
Type of programming	FB 45, FB 55, FC 56, Ident profile (PIB), (FC 45/55 with limited functionality)	FC 44	
Type of computer-mediated communication	acyclic communication	Cyclic communication	
Standards, specifications, approvals			
Certificate of suitability	CE, FCC, cULus	CE, FCC, cULus	
MTBF	122 y	122 y	
Accessories			
Accessories	Connection block for ECOFAST system or M12, 7/8"	Connection block for ECOFAST system or M12, 7/8"	

Selection and ordering data

	Article No.
ASM 456 communication module	6GT2002-0ED00
For connecting 2 readers to PROFIBUS DP-V1.	
RF160C communication module	6GT2002-0EF00
For connecting 2 readers to PROFIBUS DP-V0.	
Accessories ECOFAST connection	
ECOFAST connection block	6ES7194-3AA00-0AA0
PROFIBUS ECOFAST HYBRID plug 180	
 With male insert (5-pack) 	6GK1905-0CA00
With female insert (5-pack)	6GK1905-0CB00
PROFIBUS ECOFAST termination plug	6GK1905-0DA10
With terminating resistors.	
PROFIBUS ECOFAST hybrid	
Trailing-type cable (PUR casing) with two shielded copper cables for PROFIBUS DP and four copper cores of 1.5 mm ² each.	
Sold by the meter max. length 1 000 m; minimum order quantity 20 m.	6XV1830-7AH10
• Prefabricated with ECOFAST male and female connectors, fixed length:	
0.5 m	6XV1830-7BH05
1 m	6XV1830-7BH10
1.5 m	6XV1830-7BH15
3 m	6XV1830-7BH30
5 m	6XV1830-7BH50
10 m	6XV1830-7BN10
15 m	6XV1830-7BN15
20 m	6XV1830-7BN20
25 m	6XV1830-7BN25
30 m	6XV1830-7BN30
35 m	6XV1830-7BN35
40 m	6XV1830-7BN40
45 m	6XV1830-7BN45
50 M	6XV1830-7BN50

	Article No.
Accessories M12,	
7/8" connection	
M12 connection block, 7/8"	6ES7194-3AA00-0BA0
M12 terminating resistor for PROFIBUS	6GK1905-0EC00
Pack with 5 units, minimum ordering quantity 1 pack.	
AB THE MODERAL ESTADE OF	
PROFIBUS M12 connecting cable Pre-assembled, with 5-pin M12 connector and socket, max. length 100 m.	
10.7 M	
0.3 m	6XV1830-3DE30
0.5 m	6XV1830-3DE50
1 m	6XV1830-3DH10
1.5 m	6XV1830-3DH15
2 m	6XV1830-3DH20
3 m	6XV1830-3DH30
5 m	6XV1830-3DH50
10 m	6XV1830-3DN10
15 m	6XV1830-3DN15
7/8" plug-in cable Prefabricated, with 5-pin 7/8" connector and socket, max. length 50 m.	
6	
0.3 m	6XV1822-5BE30
0.5 m	6XV1822-5BE50
1 m	6XV1822-5BH10
1.5 m	6XV1822-5BH15
2 m	6XV1822-5BH20
3 m	6XV1822-5BH30
5 m	6XV1822-5BH50
10 m	6XV1822-5BN10
15 m	6XV1822-5BN15
Other special lengths with 90°	

or 120° cable connection, see

http://support.automation.siemens.com/WW/view/en/26999294

ASM 456, SIMATIC RF160C

	Article No.		Article No.
PROFIBUS FC Standard Cable	6XV1830-0EH10	RFID accessories	
Standard type with special design for quick mounting, 2-core, shielded, sold by the meter; maximum ordering quantity unit 1 000 m, minimum ordering quantity 20 m.		MOBY D reader cable PUR material, CMG approval, suitable for cable carriers, 2 m.	6GT2691-4FH20
		Reader cable for SIMATIC RF200 /	
PROFIBILS M12 coble connector		RF300 / RF600 / MV440	
Pack with 5 units, minimum ordering quantity 1 pack.		Or extension cable MOBY D and SIMATIC RF200 / RF300 / RF600 / MV400, PUR material,	
With male insert	6GK1905-0EA00	CMG approval, suitable for cable carriers	
With female insert	6GK1905-0EB00		
7/8" cable connector for voltage			
Pack with 5 units, minimum ordering quantity 1 pack.		COMPANY OF THE OWNER	
and an		2 m straight connector	6GT2891-4FH20
		5 m straight connector	6GT2891-4FH50
With male insert	6GK1905-0FA00	10 m straight connector	6GT2891-4FN10
With female insert	6GK1905-0FB00	20 m. straight connector	6GT2891-4FN20
Sealing caps 7/8"	6ES7194-3JA00-0AA0	50 m. straight connector	6GT2891-4FN50
For unused 24 V cable extension, pack of 10, minimum ordering quantity 1 pack.		2 m, plug angled at reade	6GT2891-4JH20
		5 m, plug angled at reade	6GT2891-4JH50
		plug angled at reade	
		Sealing caps M12 for unused reader connections	3RX9802-0AA00
Power line	6XV1830-8AH10	Minimum ordering quantity 10 units.	
5-core, 5 x 1.5 mm ² , trailing type; sold by the meter; maximum ordering quantity 1 000 m, minimum ordering quantity 20 m.		DVD "RFID Systems Software & Documentation"	6GT2080-2AA20
A Contraction of the second se	•	Dimensional drawings	
General accessories			
Stainless steel screws for connection blocks Optional screws made of V4A steel for securing the connection blocks on the basic module. For use in wet areas. Pack with 40 units is sufficient for 10 connection blocks.	6GT2090-0VB00		

ASM 456 and SIMATIC RF160C communication modules

SIMATIC RF180C / RF182C / RFID 181EIP



modules for direct connection of SIMATIC identification systems to PROFINET IO/Ethernet and Ethernet/IP. The readers (SLG) of the RFID systems MOBY D, SIMATIC RF200 / RF300 / RF600 as well as the MV400 optical reader devices (RF180C and RFID 181EIP only) can be operated on the communication modules.

Due to the high degree of protection and ruggedness, SIMATIC RF180C / RF182C and RFID 181EIP are particularly suitable for machine level use. The uniform plug-in connection system ensures rapid commissioning.

specially designed for a wide range of applications in industrial automation and logistics. Due to their high IP67 degree of protection, SIMATIC RF180C/RF182C and RFID 181EIP can be installed in the process outside the control cabinet.

Main applications for SIMATIC RF180C/RF182C and RFID 181EIP:

The Ethernet-based communication modules have been

- Mechanical engineering, automation systems, conveyor systems
- · Ancillary assembly lines in the automotive industry / suppliers
- Small assembly lines

SIMATIC RF180C / RF182C / RFID 181EIP

Design



Function

The SIMATIC RF180C/RF182C and RFID 181EIP communication modules consist of a basic module and a connection block that must be ordered separately.

The connection block is available in three versions:

• M12, 7/8" (5-pole):

PROFINET/Ethernet is connected by means of an M12 connector, the power supply is connected by means of a 5-pole 7/8" connector. There are 2 connections each for PROFINET/Ethernet as well as for the power supply. This ensures that the SIMATIC RF180C/RF182C can be connected to additional bus nodes without the need for external distributors. The removable connection block allows a base module to be replaced without interrupting the supply voltage to other bus stations.

- Push-pull connector (according to IEC 61918): PROFINET/Ethernet and the power supply are connected by means of a push-pull connector. There are 2 connections each for PROFINET/Ethernet as well as for the power supply. This ensures that SIMATIC RF180C/RF182C can be connected to additional bus nodes without the need for external distributors. The supply voltage connectors can conduct currents of up to 12 A (1L+ and 2L+). The removable connection block allows a base module to be replaced without interrupting the supply voltage to other bus stations.
- M12, 7/8" (4-pole; not recommended for RF180C): Ethernet is connected by means of an M12 connector, the power supply is connected by means of a 4-pole 7/8" connector. There are 2 connections for Ethernet and one connection is available for the power supply. This connection block can be used in applications where the 5-pole 7/8" connector is already being used for other functions and therefore cannot be used for the power supply.

A pre-assembled reader cable, available in lengths from 2 m to 50 m, is used to connect one or two readers to the communication module. The cable can also be assembled by the customer as required. The data in the transponder can in principle be accessed by direct addressing using absolute addresses.

Error messages and operating states (transponder in the field, transmission, etc.) are indicated additionally by means of LEDs and simplify commissioning and service.

The SIMATIC RF180C/RF182C and RFID 181EIP communication modules have two reader interfaces from which the readers are also supplied with voltage. In the communication module, the power supply of the readers has an electronic fuse. The maximum permissible current per communication module for the readers is 1 A. It is of no importance here whether the current is drawn by 1 or 2 readers.

SIMATIC RF180C

The SIMATIC RF180C is designed for use in PROFINET networks. SIMATIC RF180C is integrated in SIMATIC STEP 7 via the GSDML file. The SIMATIC RF180C can then be configured using the device manager of the TIA Portal or another PROFINET tool.

The application accesses the transponder via the FB 45 or via blocks from the Ident Library. The transponder is addressed using absolute addresses. For large volumes of data and complex tag operations, the FB 45 can process chained commands. The Ident Library is already integrated in the TIA Portal an doffers functions that are very easy to parameterize.

Data is exchanged between SIMATIC RF180C and the application by means of acyclic data records. This ensures that large quantities of data can be transferred from/to SIMATIC RF180C without loading the bus cycle.

Using the "RFID standard profile" setting, the RF180C can be operated directly in a SIMOTION.

SIMATIC RF182C

The SIMATIC RF182C is designed for use in Ethernet networks based on TCP/IP. The IP address of the SIMATIC RF182C is set using the "Primary Setup Tool". The RF182C is then ready for operation. This tool can be downloaded from

http://support.automation.siemens.com/WW/view/en/19440762

Communication with the SIMATIC RF182C is implemented using XML commands. XML commands have a very simple structure. This makes programming of the RF182C under any operating system very easy. The simple command command set of the RF182C can also be programmed easily in any Ethernet-capable controller.

RFID 181EIP

The communication module RFID 181EIP is designed for use in Ethernet/IP networks. A DHCP server automatically assigns an IP address to the RFID 181EIP. Alternatively, the user can assign issue static IP addresses on the DHCP server. The standard tool for assigning IP addresses is called the BOOTP/DHCP server and is included in the RSLinx software package.

The RFID 181EIP communicates with the reader by means of implicit and explicit messages. Commands and results are transferred with explicit messages. The user sets up the commands directly in the application program. Application examples are available to make getting started easier. Technical specifications

Communication modules

SIMATIC RF180C / RF182C / RFID 181EIP

Article number	6GT2002-0 ID00	6GT2002-0 ID10	6GT2002-0 ID20
Product type designation	PE180C communication module	PE182C communication module	PEID 181EIR communication module
Suitability for operation	PROFINET network together with	Industrial Ethernet network together	Ethernet/IP network together with
	RF200/300/600, MV400, MOBY D/E/I/U	with RF200/300/600, MOBY D/U	RF200/300/600, MV400, MOBY D/E/I/U
Transmission rate			
Transfer rate for Industrial Ethernet	10 100 Mbit/s	10 100 Mbit/s	10 100 Mbit/s
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s	115.2 kbit/s	115.2 kbit/s
Interfaces			
Design of the interface for point-to-point connection	RS422	RS422	RS422
Number of readers connectable	2	2	2
Type of electrical connection			
 of Industrial Ethernet interface 	(according to the connection block)	(according to the connection block)	(according to the connection block)
 for supply voltage 	(according to the connection block)	(according to the connection block)	(according to the connection block)
Design of the interface to the reader for communication	M12, 8-pin	M12, 8-pin	M12, 8-pin
Mechanical data			
Material	Thermoplastic (Valox 467, fiberglass reinforced)	Thermoplastic (Valox 467, fiberglass reinforced)	Thermoplastic (Valox 467, fiberglass reinforced)
Color	IP Basic 714	IP Basic 714	IP Basic 714
Tightening torque of the screw for securing the equipment maximum	3 Nm	3 Nm	3 Nm
Supply voltage, current consumption, power loss			
Supply voltage			
 at DC Rated value 	24 V	24 V	24 V
• at DC	20 30 V	20 30 V	20 30 V
Consumed current at DC at 24 V			
• without connected devices typical	0.1 A	0.1 A	0.1 A
 with connected devices maximum 	1.1 A	1.1 A	1.1 A
Permitted ambient conditions			
Ambient temperature			
 during operation 	0 60 °C	0 60 °C	0 60 °C
 during storage 	-40 +70 °C	-40 +70 °C	-40 +70 °C
 during transport 	-40 +70 °C	-40 +70 °C	-40 +70 °C
Protection class IP	IP67	IP67	IP67
Shock resistance	According to IEC 61131-2	According to IEC 61131-2	According to IEC 61131-2
Shock acceleration	300 m/s ²	300 m/s ²	300 m/s ²
Vibrational acceleration	100 m/s ²	100 m/s ²	100 m/s ²
Design, dimensions and weight			
Width	60 mm	60 mm	60 mm
Height	30 mm	30 mm	30 mm
Depth	210 mm	210 mm	210 mm
Net weight	0.21 kg	0.21 kg	0.21 kg
Mounting type	2 x M5 screws	2 x M5 screws	2 x M5 screws
Cable length for RS422 interface maximum	1 000 m	1 000 m	1 000 m

SIMATIC RF180C / RF182C / RFID 181EIP

Article number	6GT2002-0JD00	6GT2002-0JD10	6GT2002-0JD20
Product type designation	RF180C communication module	RF182C communication module	RFID 181EIP communication module
Product properties, functions, components general			
Display version	4 LEDs per reader connection, 4 LEDs for device status	4 LEDs per reader connection, 4 LEDs for device status	4 LEDs per reader connection, 4 LEDs for device status
Protocol is supported Media Redundancy Protocol (MRP)	No	No	No
Product function transponder file handler can be addressed	Yes	No	Yes
Protocol is supported			
• LLDP	Yes	No	No
 PROFINET IO protocol 	Yes	No	No
• TCP/IP	No	Yes	No
EtherNet/IP protocol	No	No	Yes
Type of parameterization	GSDML	XML	EDS file
Type of programming	FB 45, FB 55, Ident profile (PIB)	XML commands	Data records via implicit/explicit mes- sages
Type of computer-mediated communication	acyclic communication	XML	Implicit/explicit messaging
Standards, specifications, approvals			
Certificate of suitability	CE, FCC, cULus, PNO: Conformance Class B	CE, FCC, cULus	CE, FCC, cULus
MTBF	121 y	121 y	121 y
Accessories			
Accessories	Connection block M12 d-coded, 7/8" 5-pin or push-pull	Connection block M12 d-coded, 7/8" 5-pin or push-pull or M12 d-coded, 7/8" 4-pin	Connection block M12 d-coded, 7/8" 5-pin or push-pull or M12 d-coded, 7/8" 4-pin
SIMATIC RF180C / RF182C / RFID 181EIP

Selection and ordering data

	Article No.		Article No.
SIMATIC RF180C communication module	6GT2002-0JD00	Accessories for network connection M12, 7/8" (5-pole)	
For PROFINET, for connecting 2 readers, without a connection block.		IE connecting cable M12-180/M12-180 Pre-assembled JE EC TP	
SIMATIC RF182C communication module	6GT2002-0JD10	trailing cable GP 2x2 (PROFINET Type C), with two 4-pin M12 plugs	
For Ethernet, for connecting 2 readers, without a connection block.		IP65/IP67 degree of protection.	
RFID 181EIP communication module	6GT2002-0JD20		
For Ethernet/IP, for connecting 2 readers, without a connection block.		E BAR	
Connection block	6GT2002-1JD00	0.3 m	6XV1870-8AE30
For SIMATIC RF180C/RF182C,		0.5 m	6XV1870-8AE50
		1 m	6XV1870-8AH10
arman com		1.5 m	6XV1870-8AH15
		2 m	6XV1870-8AH20
		3 m	6XV1870-8AH30
		5 m	6XV1870-8AH50
		10 m	6XV1870-8AN10
		15 m	6XV1870-8AN15
Connection block For SIMATIC RF180C/RF182C,	6GT2002-2JD00	7/8" connecting cable to power supply	
		Pre-assembled with two 5-pin 7/8" male and female connectors.	
		0.3 m	6XV1822-5BE30
Connection block	6GT2002-4.ID00	0.5 m	6XV1822-5BE50
For SIMATIC RF182C, RFID 181EIP,		1 m	6XV1822-5BH10
M12 d-coded, 7/8" (4-pole).		1.5 m	6XV1822-5BH15
		2 m	6XV1822-5BH20
		3 m	6XV1822-5BH30
® ®		5 m	6XV1822-5BH50
		10 m	6XV1822-5BN10
		15 m	6XV1822-5BN15
		Other special lengths with 90° or 120° cable connection, see	

http://support.automation.siemens.com/WW/view/en/26999294

SIMATIC RF180C / RF182C / RFID 181EIP

	Article No.		Article No.
PROFINET M12 plug-in connectors	6GK1901-0DB20-6AA0	Accessories for push-pull RJ45 network connection	
Rugged metal housing; axial cable outlet; D-coded.		Push-pull cable connector for 1L+/2L+	6GK1907-0AB10-6AA0
		Unassembled.	
		Push-pull cable connector for RJ45	6GK1901-1BB10-6AA0
		Unassembled.	
7/8" cable connector, for voltage		Cover caps for push-pull female connectors	6ES7194-4JA50-0AA0
Pack with 5 units, minimum ordering quantity 1 pack		(1L+/2L+), pack of 5.	
		Cover caps for push-pull female connectors	6ES7194-4JD50-0AA0
and the		RJ45, pack of 5.	
		Accessories for network connection M12, 7/8" (4-pole)	
With male insert	6GK1905-0FA00	Network wiring with M12	Accessories, as for M12, 7/8" (5-pole)
With female insert	6GK1905-0FB00	Power supply with 7/8" (4-pole)	No cables and connectors from Siemens
IE M12 control cabinet bushing	6GK1901-0DM20-2AA5	Accessories for PROFINET bus components	
For conversion from M12 (D-coded) to RJ45, pack with 5 units		SCALANCE XB205-3	6GK5205-3BD00-2AB2
minimum ordering quantity 1 pack.		With five 10/100 Mbps RJ45 ports and three fiber-optic cable ports	
		(MM FO SC). Description see page 5/28.	
IE Connecting Cable M12-180/ IE FC RJ45 Plug 145 Prefabricated IE FC TP trailing cable GP 2 x 2 (PROFINET type C) with M12 plug (D-coded) and JE C B J45 plug			
IP65/IP67 degree of protection.		SCALANCE X204IRT PRO Industrial Ethernet switch	6GK5204-0JA00-2BA6
		with four 10/100 Mbps RJ45 push-pull ports. Description see page 5/27.	
2 m	6XV1871-5TH20		
3 m	6XV1871-5TH30		
5 m	6XV1871-5TH50		
10 m	6XV1871-5TN10		
15 m	6XV1871-5TN15		
IE FC RJ45 PLUG 180 RJ45 plug	6GK1901-1BB10-2AA0		
With rugged metal housing and FC connection system, straight cable outlet.		IE FC TP standard cable GP 2x2	6XV1840-2AH10
		cable for connection to IE, FC outlet RJ45/IE FC RJ45 plug, PROFINET-compatible, with UL approval, sold by the meter, max. delivery unit 1 000 m, minimum ordering quantity 20 m	
Sealing caps 7/8" Pack with 10 units, minimum ordering quantity 1 pack.	6ES7194-3JA00-0AA0		
		24	

Siemens ID 10 · 2016

SIMATIC RF180C / RF182C / RFID 181EIP Article No. Dimensional drawings 6XV1830-8AH10 Power line 5-core, 5 x 1.5 mm², trailing type, 60 28 ordering quantity 20 m, maximum ordering quantity 1 000 m. 0 **RF180C** ۵ ۵ ۵ ۵ SIMATIC \odot ۵ 100 ٥ ۵ ٥ General accessories ۵ ٥ 210 -Stainless steel screws 6GT2090-0VB00 ۵ 0 for connection blocks 0000 ٥ ۵ Optional screws made of V4A steel for securing the connection blocks on the basic module. For use in <u>z</u>Q ۵ SIMATIC RF180C CE wet areas. Pack with 40 units is sufficient for 10 connection blocks. ۵ FS10_90115 ۵ 75 4 500 ì 24 **RFID** accessories SIMATIC RF180C, RF182C, RFID 181EIP communication module MOBY D reader cable 6GT2691-4FH20 PUR material, CMG approval, suitable for cable carriers, 2 m. Reader cable for SIMATIC RF200 / RF300 / RF600 / MV440 or extension cable MOBY D and SIMATIC RF200 / RF300 / RF600 / MV400, PUR material, CMG approved, suitable for cable carriers 2 m, straight connector 6GT2891-4FH20 6GT2891-4FH50 5 m, straight connector 10 m, straight connector 6GT2891-4FN10 6GT2891-4FN20 20 m, straight connectore 6GT2891-4FN50 50 m, straight connector 2 m, 6GT2891-4JH20 plug angled at reader 5 m, 6GT2891-4JH50 plug angled at reader 10 m, 6GT2891-4JN10 plug angled at reader Sealing caps M12 for 3RX9802-0AA00 unused reader connections Minimum ordering quantity 10 units. DVD "RFID Systems Software & 6GT2080-2AA20 Documentation⁴

SIMATIC RF170C

Overview



The SIMATIC RF170C is a communication module for connecting the SIMATIC identification systems to the ET 200pro distributed I/O system. The readers (SLGs) of all RFID systems as well as the MV400 code-reading systems can be operated on the SIMATIC RF170C.

Thanks to the high degree of protection and ruggedness, ET 200pro is particularly suitable for machine-level use. The modular structure with PROFIBUS and PROFINET connection systems allows them to be used in all applications. The uniform plug-in connection system ensures rapid commissioning.

Benefits

9 Get Designed for Industry

- Two parallel reader channels ensure real-time mode at dynamic read points.
- Through selection of the corresponding head module, a connection of the RFID systems via PROFIBUS or PROFINET is possible.
- The modular design with interface modules for PROFIBUS and PROFINET supports universal implementation.
- Reader connection using an 8-pin M12 connector for quick mounting of all components.
- Powerful hardware guarantees rapid data exchange with the reader (SLG) so that data is made available to the application even faster.
- Very easy downloading of firmware via the SIMATIC Manager for function expansions and error rectification ensure high availability of the identification system.
- Adjustable and parameterizable identification-systemspecific diagnostics facilitate easy commissioning and troubleshooting.
- A wide selection of pre-assembled connecting cables can be ordered for ET 200pro and SIMATIC RF170C. This saves time and money during installation and assures better quality.

Application

The ET 200pro distributed I/O system with the SIMATIC RF170C communication module has been specially designed for a wide range of applications in industrial automation and logistics. Thanks to the high degree of protection of IP67, the SIMATIC RF170C can be installed without a control cabinet.

Used primarily for the SIMATIC RF170C:

- Mechanical engineering, automation systems, conveyor systems
- Ancillary assembly lines in the automobile industry/suppliers
- Small assembly lines

Design



SIMATIC RF170C communications module

SIMATIC RF170C

Function

The SIMATIC RF170C comprises an electronics module and a connection block that must be ordered separately. The interface module is available in PROFIBUS or PROFINET version.

- For the PROFIBUS connection, you can choose between ECOFAST, M12, 7/8" or screwed cable gland for the connection system.
- For the PROFINET interface module, the M12, 7/8" or push pull (RJ45 or SCRJ FO) connection system is available.

Integration of SIMATIC RF170C into SIMATIC STEP 7 is already implemented in the TIA Portal but can also be accomplished by means of a Hardware Support Package (HSP). The GSD file of the ET 200pro system is available for integration into non-Siemens systems.

A pre-assembled reader cable, available in lengths from 2 m to 50 m, is used to connect one or two readers to the communication module. The cable can also be assembled by the customer as required.

The data in the transponder is accessed by direct addressing using absolute addresses.

Error messages and operating states (transponder in the field, transmission, etc.) are indicated additionally by means of LEDs and simplify commissioning and service.

The SIMATIC RF170C has two reader interfaces from which the readers are also supplied with power. In the SIMATIC RF170C, the power supply for the readers has an electronic fuse. The maximum permissible current per SIMATIC RF170C for the readers is 0.8 A. It is of no importance here whether the current is drawn by one or two readers.

The data in the transponder or on the data matrix code can be accessed direct using absolute addresses (FB/FC 45, FB/ FC 55). When the ET 200pro is operated with a PROFINET interface, use of the FB (FB 45, FB 55) is mandatory. The RF170C also supports the functions of the Ident Library. The Ident Library is already integrated in the TIA Portal an doffers functions that are very easy to parameterize.

Communication between the SIMATIC RF170C and the controller is acyclic. Consequently, a very large amount of data can be transferred to/from the SIMATIC RF170C without overloading the bus cycle. This has advantages when transferring large volumes of data. The SIMATIC RF170C can also process concatenated transponder commands very quickly in this mode.

Notice: When connecting high-speed RFID systems (e.g. RF300), the data throughput can decrease due to the distributed configuration of the ET 200pro. Therefore use the data throughput calculation tool when configuring. You can find the tool on the DVD with article number 6GT2080-2AA20.

Technical specifications

Article number	6GT2002-0HD00
Product type designation	RF170C communication module
Suitability for operation	Distributed IO ET 200pro together with RF200/300/600, MV300/400, MOBY D/E/I/U and RS232 devices
Transmission rate	
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s
Interfaces	
Design of the interface for point-to-point connection	RS422/RS232 via connection block
Number of readers connectable	2
Type of electrical connection	
 of the backplane bus 	ET 200pro backplane bus
 of the PROFIBUS interface 	(according to the head module)
 of Industrial Ethernet interface 	(according to the head module)
 for supply voltage 	ET 200pro backplane bus
Design of the interface to the reader for communication	Internal plug to the connection block
Mechanical data	
Material	Thermoplastic (Valox 467, fiberglass reinforced)
Color	IP Basic 714
Tightening torque of the screw for securing the equipment maximum	1.5 Nm
Supply voltage, current consumption, power loss	
Supply voltage	
at DC Rated value	24 V
• at DC	20 30 V
Consumed current at DC at 24 V	
 without connected devices typical 	0.13 A
with connected devices maximum	1 A
Permitted ambient conditions	
Ambient temperature	
 during operation 	-25 +55 °C
during storage	-40 +70 °C
during transport	-40 +70 °C
Protection class IP	IP67
Shock resistance	
	According to IEC 61131-2
Shock acceleration	According to IEC 61131-2
Shock acceleration	According to IEC 61131-2 300 m/s ²
Shock acceleration Vibrational acceleration	According to IEC 61131-2 300 m/s ² 100 m/s ²
Shock acceleration Vibrational acceleration Design, dimensions and weight	According to IEC 61131-2 300 m/s ² 100 m/s ²
Shock acceleration Vibrational acceleration Design, dimensions and weight Width	According to IEC 61131-2 300 m/s ² 100 m/s ² 90 mm
Shock acceleration Vibrational acceleration Design, dimensions and weight Width Height	According to IEC 61131-2 300 m/s ² 100 m/s ² 90 mm 130 mm 25 mm
Shock acceleration Vibrational acceleration Design, dimensions and weight Width Height Depth Nat weight	According to IEC 61131-2 300 m/s ² 100 m/s ² 90 mm 130 mm 35 mm 0.27 km
Shock acceleration Vibrational acceleration Design, dimensions and weight Width Height Depth Net weight	According to IEC 61131-2 300 m/s ² 100 m/s ² 90 mm 130 mm 35 mm 0.27 kg
Shock acceleration Vibrational acceleration Design, dimensions and weight Width Height Depth Net weight Mounting type	According to IEC 61131-2 300 m/s ² 100 m/s ² 90 mm 130 mm 35 mm 0.27 kg ET 200pro rack

SIMATIC RF170C

Article number	6GT2002-0HD00
Product type designation	RF170C communication module
Product properties, functions, components general	
Display version	(see connection block)
Product function transponder file handler can be addressed	No
Protocol is supported	
 S7 communication 	Yes
Type of parameterization	HSP
Type of programming	FB 45, FB 55, ident profile, (FC 45/55 with limited functionality)
Type of computer-mediated communication	acyclic communication
Standards, specifications, appro- vals	
Certificate of suitability	CE, FCC, cULus
MTBF	77 у
Accessories	
Accessories	Connection block for RF170C

Selection and ordering data

	Article No.
SIMATIC RF170C communication module	6GT2002-0HD00
For connecting to the distributed I/O system ET 200pro	
Accessories	
Connection block for SIMATIC RF170C	6GT2002-1HD00
For connecting 2 readers via an M12 connector	
Reader cable for SIMATIC RF200 / RF300 / RF600 / MV440 Or extension cable MOBY D and SIMATIC RF200 / RF300 / RF600 / MV400, PUR material, CMG approved, suitable for cable carriers	

San Car

2 m, straight connector 5 m, straight connector 10 m, straight connector 20 m, straight connector 50 m, straight connector 2 m, plug angled at reader 5 m, plug angled at reader 10 m, plug angled at reader 6GT2891-4FH20 6GT2891-4FH50 6GT2891-4FN10 6GT2891-4FN20 6GT2891-4FN50 6GT2891-4JH20 6GT2891-4JH50 6GT2891-4JN10



Dimensional drawings



SIMATIC RF170C communications module



Connector block for SIMATIC RF170C

Overview



The SIMATIC RF120C is a communication module for connecting the SIMATIC identification systems directly to the SIMATIC S7-1200. The readers of all RFID systems as well as the MV400 optical readers can be operated on the SIMATIC RF120C

Integration into the TIA Portal and the uniform plug-in connection systems permit fast and simple commissioning.

Benefits



- · Space savings thanks to the extremely compact design of the identification system connected directly to the controller
- Due to the intuitive parameterization of the RF120C and the reader via the SIMATIC device configuration, the manual is mostly no longer required.
- The Ident Library is integrated in the TIA Portal and offers Ident instructions (e.g. Read, Write) that are very easy to use and thus facilitate programming and commissioning without the need for documentation.
- Reader connection using a sub-D connector on the RF120C for fast installation of all components
- Powerful hardware ensures maximum data exchange speed with the reader so that data is made available to the application even faster.
- Very easy downloading of functional expansion and error rectification firmware for RF120C and readers via the TIA Portal ensures high availability of the identification system

Application

The SIMATIC S7-1200 controller with the RF120C communication module has been developed for all simple control applications including identification tasks.

Due to its technical setup with IP 20 degree of protection, the S7-1200 is designed for use in the control cabinet.

Main applications for SIMATIC RF120C:

- · Mechanical engineering, automation systems, conveyor systems
- Ancillary assembly lines in the automobile industry/suppliers
- Small assembly lines

Design SIMATIC S7-1200 with RF120C \bigcirc \bigcirc Transponder Reader G_FS10_XX_00456

SIMATIC RF120C communication module

Function

The SIMATIC RF120C communications module is positioned to the left of the S7-1200 CPU. It enables a maximum of three RF120Cs to be operated on one S7-1200 CPU.

The reader is powered from the RF120C. The RF120C is provided with voltage via a screw-type terminal connector which is included in the scope of delivery.

For programming in the controller, a library is available with simple instructions such as Read/Write for accessing the transponder data. These instructions can also be used for other identification communication modules that are connected to the S7-1200 via Profibus/Profinet, e.g. for ASM 456 and RF180C Furthermore, the library blocks can also be used for the SIMATIC S7-1500 so that the identification communication modules can be operated there via Profibus/Profinet.

Error messages and operating states (transponder in the field, transmission, etc.) are indicated additionally by means of LEDs behind the top cover of the RF120C. This makes commissioning and servicing considerably easier.

The RF120C features a sub D socket for connecting the reader. This also supplies the reader with voltage. The power supply of the reader is equipped with an electronic fuse. The maximum permissible current for a reader is 1 A.

The reader is connected to the RF120C with a pre-assembled reader cable which is available in different lengths. This 6GT2091-4Lxxx type cable can easily be extended with a type 6GT2891-4Fxxx cable in order to cover greater distances between the reader and the controller.

Communication between the SIMATIC RF120C and the controller is acyclic. Consequently, a very large amount of data can be transferred to/from the RF120C without overloading the bus cycle. This has advantages when transferring large volumes of data

SIMATIC RF120C

Technical specifications

Article number	6GT2002-0LA00
Product type designation	RF120C communication module
Suitability for operation	SIMATIC S7-1200 together with RF200/300/600, MV400, MOBY D/U
Transmission rate	
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s
Interfaces	
Design of the interface for point-to- point connection	RS422
Number of readers connectable	1
Type of electrical connection	
 of the backplane bus 	S7-1200 backplane bus
 for supply voltage 	Screw terminals
Design of the interface to the reader for communication	D-sub, 9-pin, socket
Mechanical data	
Material	Xantar MX 1094
Color	Ti-grey 24L01
Tightening torque of the screw for securing the equipment maximum	0.45 Nm
Supply voltage, current	
Supply voltage	
at DC Bated value	24 V
• at DC	20 30 V
Consumed current at DC at 24 V	20 00 V
without connected devices typical	0.03 A
with connected devices maximum	1 A
Permitted ambient conditions	
Ambient temperature	
during operation	0 55 °C
during storage	-40 +70 °C
 during transport 	-40 +70 °C
Protection class IP	IP20
Shock resistance	According to IEC 61131-2
Shock acceleration	300 m/s ²
Vibrational acceleration	100 m/s ²
Design, dimensions and weight	
Width	30 mm
Height	100 mm
Depth	75 mm
Net weight	0.15 kg
Mounting type	S7-1200 rack
Cable length for RS422 interface maximum	1 000 m
Product properties, functions, components general	
Display version	4 LEDs for reader connection, 1 LED for device status
Product function transponder file handler can be addressed	No
Protocol is supported	
S7 communication	Yes
Type of parameterization	HSP
Type of programming	Library with functions
Type of computer-mediated communication	acyclic communication
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, cULus, KCC, C-Tick, FM, Ex: II 3G Ex nAA IIC T4 Gc
MTBF	196 y

Selection and ordering data

	Article No.
SIMATIC RF120C communication module	6GT2002-0LA00
Integrated in the S7-1200 controller for connection of a reader	
Accessories for all readers	
Reader cable for SIMATIC RF200 / RF300 / RF600 / MV400	
PUR material, CMG approval, suitable for cable carriers, straight reader connector	
2 m	6GT2091-4LH20
5 m	6GT2091-4LH50
10 m	6GT2091-4LN10
Accessories for extended us	
Extension cable for all readers	
PUR material, CMG approval, suitable for cable carriers	
in the second second	
a a second	
Con Francisco Con Constantino	
2 m, straight connector	6GT2891-4FH20
5 m, straight connector	6GT2891-4FH50
10 m, straight connector	6GT2891-4FN10
20 m, straight connector	6GT2891-4FN20
50 m, straight connector	6GT2891-4FN50
2 m, plug angled at reader	6GT2891-4JH20
5 m, plug angled at reader	6GT2891-4JH50
10 m, plug angled at reader	6GT2891-4JN10
Reader adapter cable for MOBY D Material PUR, CMG approval, suitable for cable carriers, 2 m. A cable of the type 6GT2091-4L is also required.	6GT2691-4FH20
DVD "RFID Systems Software & Documentation"	6GT2080-2AA20

SIMATIC RF120C

Dimensional drawings



SIMATIC RF120C communication module

ASM 475

Overview



The ASM 475 is a powerful communication module for connecting the MOBY D, SIMATIC RF200, RF300, RF600 and SIMATIC MV400 identification systems to the S7-300 and ET 200M.

Application

The ASM 475 communication module integrates the identification systems into the following automation systems:

- SIMATIC S7-300
- S7-400, PC (CP5412 (A2)) over ET 200M
- SINUMERIK 840D/810D

A maximum of two readers can be connected in parallel and operated in parallel mode.

Design



Function

As many as 8 ASM 475 communication modules can be plugged into one SIMATIC S7-300 rack and operated. For a multi-rack installation (maximum of 4), the ASM 475 communication modules can be plugged in and operated in each rack. This means that as many as 32 ASM 475s can be operated in the maximum configuration of a SIMATIC S7-300. The electrical isolation between the reader and SIMATIC S7-300 bus ensures a noise-resistant setup.

Error messages and operating states (transponder in field, command active, etc.) are indicated using LEDs.

Communication between the ASM 475 and S7-CPU takes place by means of acyclic P-bus message frames so that the useful data is transmitted very quickly and effectively. The ASM 475 is fully integrated into the diagnostics of the SIMATIC via a hardware support package (HSP). Depending on the PROFIBUS master, as many as 126 ET 200M modules can be operated on one PROFIBUS line.

The data in the transponder or Data Matrix Code is accessed direct by means of physical addresses using the ASM 475. The data is transferred between FB/FC 45, FB/FC 55 and ASM 475 at high speed and without placing a great load on the CPU.

ASM 475

Technical specifications

Article number	6GT2002-0GA10
Product type designation	ASM 475 communication module
Suitability for operation	SIMATIC S7-300, ET 200M together with RF200/300/600, MOBY D/E/I/U
Transmission rate	
Transfer rate at the point-to-point connection serial maximum	115.2 kbit/s
Interfaces	
Design of the interface for point-to-point connection	RS422
Number of readers connectable	2
Type of electrical connection	
 of the backplane bus 	S7-300 backplane bus
 of the PROFIBUS interface 	(according to the head module)
 of Industrial Ethernet interface 	(according to the head module)
 for supply voltage 	Screw-type or spring-loaded terminals
Design of the interface to the reader for communication	Screw-type or spring-loaded terminals
Mechanical data	
Material	Noryl
Color	anthrazit
Supply voltage, current consumption, power loss	
Supply voltage	
 at DC Rated value 	24 V
• at DC	20 30 V
Consumed current at DC at 24 V	
 without connected devices typical 	0.1 A
with connected devices maximum	1 A
Permitted ambient conditions	
Ambient temperature	
 during operation 	0 60 °C
 during storage 	-40 +70 °C
 during transport 	-40 +70 °C
Protection class IP	IP20
Shock resistance	According to IEC 61131-2
Shock acceleration	150 m/s ²
Vibrational acceleration	10 m/s ²
Design, dimensions and weight	
Width	40 mm
Height	125 mm
Depth	120 mm
Net weight	0.2 kg
Mounting type	S7-300 rack
Cable length for RS422 interface maximum	1 000 m

Article number	6GT2002-0GA10
Product type designation	ASM 475 communication module
Product properties, functions, components general	
Display version	4 LEDs per reader connection, 2 LEDs for device status
Product function transponder file handler can be addressed	Yes
Protocol is supported	
 S7 communication 	Yes
Type of parameterization	Object manager, GSD
Type of programming	FB 45, FB 55, FC 56 (FC 45/55 with limited functionality)
Type of computer-mediated communication	acyclic communication
Standards, specifications, approvals	
Certificate of suitability	CE, FCC, UL/CSA
Accessories	
Accessories	Front connector with screw-type or spring-loaded terminals

ASM 475

Selection and ordering data

	Article No.
ASM 475 communication module	6GT2002-0GA10
For SIMATIC S7-300 and ET 200M, parameterizable	
Accessories	
Front connector (1 x per ASM 475)	
 with screw terminals 	6ES7392-1AJ00-0AA0
 with spring-loaded terminals 	6ES7392-1BJ00-0AA0
Shield connecting element (80 mm wide for 2 x ASM 475)	6ES7390-5AA00-0AA0
Shield connection clamp (1 x per reader cable)	6ES7390-5BA00-0AA0
MOBY D connecting cable pre-assembled, between ASM 475 and reader D1xS, 9-pole Sub-D plug, PUR material, CMG approved, suitable for cable carriers	
5 m	6GT2491-4EH50
20 m	6GT2491-4EN20
50 m	6GT2491-4EN50
Extension cable SIMATIC RF200 / RF300 / RF600 / MV400, PUR material, CMG approval, suitable for cable carriers, straight connector	
Comments of the second se	
2 m	6GT2891-4FH20

		Article No.
	SIMATIC RF200 / RF300 / RF600 / MV400 connecting cable pre-assembled, between the ASM 475 and RF200 / RF300 / RF600 / MV400, IP65, straight connector, PUR material, suitable for cable carriers, CMG approval, in the following lengths ¹ :	
	2 m 5 m	6GT2891-4EH20 6GT2891-4EH50
	DVD "RFID-Systems Software & Documentation"	6G12080-2AA20
)		



G_FS10_XX_90112

2 m	6GT2891-4FH20
5 m	6GT2891-4FH50
10 m	6GT2891-4FN10
20 m	6GT2891-4FN20
50 m	6GT2891-4FN50

ASM 475 communication module

 The connecting cables can be extended using RF300 connecting cables of type 6GT2891-4Fxxx. These connecting cables are available in the lengths 2 m, 5 m, 10 m, 20 m and 50 m.

RFID standard cables

Overview



RFID standard cable that is used with SIMATIC RFID systems preassembled in various lengths.

Benefits



Due to the cETLus certification with CMG test and marking, the cable can also be installed in fire protection critical building parts (e.g. vertical installation in a cable duct).

The SIMATIC RFID standard cable can also be used in dynamic applications such as tow chains with a minimum bending radius of 75 mm.

Application

In addition to the normal areas of application in industry, the cable can also be laid:

- In areas subject to high heat
- For highly flexible applications (e.g. in cable carriers)
- In oil-contaminated industrial environments
- In outdoor applications exposed to solar radiation (UV radiation)

Technical specifications

Product type designation	SIMATIC RFID standard cable
Product description	Highly flexible communication line (6-wire)
Also suitable for use	in continuous motion applications, such as with drag chains
Cable designation	L-YC11Y 6x1x0.25 6x24AWG CMG
Electrical data	
Loop resistance per length/maximum	160 Ω/km
Mechanical data	
Number of electrical wires	6
Type of screen	Tin-plated braided shield made of copper wires with 0.13 mm diameter (36 AWG)
Wire diameter of the AWG24 wire	0.70 mm
Outer diameter	
 of the inner conductor 	0.70 mm
 of the wire insulation 	1.2 mm
 of the cable sheath 	5.4 mm
Symmetrical tolerance of the outer diameter/of the cable sheath	0.2 mm
Material	
 of the wire insulation 	PVC
 of the cable sheath 	PUR

Product type designation	SIMATIC RFID standard cable
Color	
 of the data wire insulation 	white / yellow / gray / pink / brown / green
 of the cable sheath 	Black
Bending radius	
 for one-off bending / minimum permissible 	21,6 mm
 for repeated bending / minimum permissible 	43 mm
 with continuous bending 	75 mm
Number of bending cycles	3 million
Number of bending cycles / note	Suitable as trailing cable for 3 million bending cycles with a bending radius of 75 mm
ensile load / maximum	200 N
Permitted ambient conditions	
Ambient temperature	
 during operation 	-30 °C 80 °C
 during storage 	-30 °C 80 °C
 during transport 	-30 °C 80 °C
 during installation 	-30 °C 80 °C
Ambient temperature / comment	Electrical properties measured at 20 °C
Behavior in fire	Flame-retardant acc. to IEC 60332-1-2
Resistance	
 to mineral oil 	resistant
• to grease	resistant
 Radiological resistance / to UV radiation 	resistant
Product properties, functions, components / general	
Halogen-free	No
Silicon-free	Yes
Standards, specifications, approvals	
 UL listing / at 300 V rating 	Yes: CMG
 UL listing / at 600 V rating 	No

Selection and ordering data

	Article No.		Article No.
MOBY D, connecting cable ASM 475 - SLG D1xS		RF200/300/600, connecting cable ASM 456, RF160C, RF170C, DE1000, RF160C, and antical	
5 m	6GT2491-4EH50	code reader device	
20 m	6GT2491-4EN20	Can also be used as	
50 m	6GT2491-4EN50	RF200/300/600, MOBY D extension cable to ASM 456, RF160C.	
MOBY D, connecting cable PC (RS232) - SLG D1x		RF170C, RF180C, RF182C, straight connector	
		2 m	6GT2891-4FH20
5 m	6GT2691-4BH50	5 m	6GT2891-4FH50
20 m	6GT2691-4BN20	10 m	6GT2891-4FN10
MOBY D, connecting cable		20 m	6GT2891-4FN20
ASM 456, RF160C, ŘF170C, RF180C, RF182C - SLG D1xS		50 m RF300, connecting cable	6GT2891-4FN50
		PC (RS232) - RF380R 5 m; 24 V connection with M12 plug	6GT2891-4KH50
2 m	6GT2691-4FH20		
RF200/300/600, connecting cable ASM 475 - reader		and the second s	
		5 m; 24 V connection with open ends	6GT2891-4KH50-0AX0
2 m	6GT2891-4EH20		
5 m	6GT2891-4EH50		
BE200/300/600.		al are	
RF120C connecting cable		Accessories	
		Connecting cable, communication module - reader, without connector	
		50 m	6GT2090-4AN50
2 m	6GT2091-4LH20	120 m	6GT2090-4AT12
5 m	6GT2091-4LH50	800 m	6GT2090-4AT80
10 m	6GT2091-4LN10	M12 connector, 8-pin	
RF200/300/600, M12 connecting cable ASM 456, RF160C, RF170C, PE182C, perfector, RF170C,		with screw-type terminal, for max. 0.5 mm ² wires.	
Reader connector, angled		Ordering quantity 5 units or multiples thereof.	
, i g		Eemale for Reader	6GT2090-0BD00
		Male for communication modules ASM 456, RF160C, RF170C, RF160C, RF160C, RF170C,	6GT2090-0BE00
2 m	6GT2891-4JH20	M12 connector 4 rin	
5 m	6GT2891-4JH50	witz connector, 4-piñ	0GR 1907-000 10-0AA3
10 m	6GT2891-4JN10		
		Male with screw-type terminal for wide-range power supply (see page 2/125).	
		I AUN ULU.	

Introduction

Overview



SCALANCE X Industrial Ethernet switches

The SCALANCE product family is designed primarily for use in diverse industrial applications.

It provides everything for ultra efficient industrial networks and bus systems: Powerful, future-proof network components for reliable operation in any type of industrial environment:

- A cabling system for fast, pre-assembled connection on site.
- · Fast redundancy for high availability.
- Process fault diagnostics for permanent monitoring of the network components.

The SCALANCE network components are characterized by:

- Comprehensive portfolio tailored to data communication requirements in different industries.
- Coordinated network components from a single source.
- Conformity according to global standards, e.g. IEEE 802.3, IEEE 802.11n.
- Integration in the TIA Portal.
- · Future-proof and innovative technology.
- 5-year warranty on all SCALANCE products with delivery date as of January 1, 2015

SCALANCE offers a comprehensive portfolio of integrated industrial communication solutions. With this portfolio, you will find the perfect connection for every industrial application – from the automotive to the chemical industry, as well as in OEM manufacturing and process industries.

SCALANCE product family

SCALANCE X – Industrial Ethernet switches

A graded portfolio of Industrial Ethernet switches in different designs and performance classes enables optimum solutions for all types of switching tasks – not only in harsh industrial environments.

SCALANCE W - Industrial Wireless LAN

Wireless communication with Industrial Wireless LAN (IWLAN) opens up more flexibility in network planning and even provides protection against failures with respect to personnel and machine safety.



Industrial Wireless LAN SCALANCE W

SCALANCE M - Industrial modems and routers

Network widely distributed plants or machines with a wide range of modems and routers - via telephone, mobile wireless or Internet, depending on requirements.



SCALANCE S - Industrial Security

The Industrial Security product portfolio offers security solutions specifically for industrial automation technology to avoid risks with respect to data security.



Selection Tools

To help you find the right Industrial Ethernet switches, configure modular versions, and select SIMATIC Ident devices, the TIA Selection Tool is available at:

http://www.siemens.com/tia-selection-tool

Industrial Ethernet Switches SCALANCE X

Overview

With the SCALANCE X product family, Siemens offers a wide range of switches for industrial use. They can be used for all Ethernet-based SIMATIC Ident devices (e.g. MV400 optical reader, RF600 reader, RF180C communication module) to establish the network architecture.

Some of the switches recommended by Siemens are listed under the accessories for the SIMATIC Ident devices (e.g. the SCALANCE X108PoE Industrial Ethernet with the MV440 optical reader).

In this section, you can find an extract from the SCALANCE portfolio as a supplement.

You can find more information and the entire portfolio of SCALANCE switches, cables and network accessories, with the associated order numbers, in the Catalog IK PI.

Product versions



SCALANCE XB005 and SCALANCE XB008 SCALANCE XB005G and SCALANCE XB008G (Gigabit)

- Unmanaged switches for setting up Industrial Ethernet networks in line and star structures
- Enclosure for space-saving installation in control cabinets or boxes on a standard mounting rail
- SCALANCE XB005 and SCALANCE XB008 5 or 8 x 10/100 Mbps RJ45 ports, electrical
- SCALANCE XB005G and SCALANCE XB008G (Gigabit) 5 or 8 x 10/100/1 000 Mbps RJ45 ports, electrical
- SCALANCE X10 unmanaged switches for setting up Industrial Ethernet networks in line and star structures
- Enclosure for space-saving installation in control cabinets or boxes on standard mounting rails
- SCALANCE XB005 and SCALANCE XB008 5 or 8 x 10/100 Mbps RJ45 ports, electrical
- SCALANCE XB005G and SCALANCE XB008G (Gigabit) 5 or 8 x 10/100/1 000 Mbps RJ45 ports, electrical

SCALANCE X108PoE

- Unmanaged switches for setting up electrical Industrial Ethernet star and line topologies
- with eight electrical ports, two of which have Power-over-Ethernet functionality
- Diagnostics on the device using LEDs (power, link status, data traffic) and signaling contact (message screen can be set using a button on the device)
- The RJ45 ports are suitable for industrial use and have additional retaining collars: Optimized for connecting the IE FC RJ45 Plug 180.



SCALANCE XB-200

- Managed switches for setting up 10/100 Mbps Industrial Ethernets in a line, star or ring topology (RM integrated)
- Electrical and optical nodes or network connections can be implemented by means of 8 or 16 RJ45 ports (10/100 Mbps) or 3 fiber-optic ports (100 Mbps)
- SCALANCE XB208; 8 x 10/100 Mbps RJ45 port, electrical
- SCALANCE XB205-3; 5 x 10/100 Mbps RJ45 port, electrical; 3 x 10/100 Mbps ports, fiber-optic cable
- SCALANCE XB216; 16 x 10/100 Mbps RJ45 port, electrical
- Rugged plastic enclosure
- Diagnostics on the device by means of LEDs (power, link status, data communication)
- The devices feature SNMP access, integral web server remote diagnostics and signaling over the network
- Diagnostics and parameter assignment via website or console port
- Supports both PROFINET and Ethernet/IP industrial protocols in the same device (software-switchable)
- All device versions available with default setting for both PROFINET and Ethernet/IP

Industrial Ethernet Switches SCALANCE X

Benefits

Get Designed for Industry

SCALANCE XB005 and SCALANCE XB008 SCALANCE XB005G and SCALANCE XB008G (Gigabit) SCALANCE X108PoE

- Implementation of simple and low-cost machine networking
- Space-saving installation thanks to small, compact design
- Can be used in industrial environments
- Quick commissioning without configuration
- · Easy on-site diagnostics via LEDs
- Use of uncrossed connecting cables possible thanks to the integrated auto crossover function
- Reduction of network installation costs by transmitting data and energy (Power-over-Ethernet) via the conventional 4-core Industrial Ethernet cable (only SCALANCE X108PoE), for example, for MV400 optical reader
- Additional power supply units can be omitted thanks to generating the Power-over-Ethernet voltage (48 V DC) direct at the switch (SCALANCE X108PoE only), for MV400 optical reader, for example.

SCALANCE XB-200

- Ideal solution for configuring Ethernet line, ring and star topologies
- High network availability due to design of redundant ring structures on the basis of high-speed redundancy (HRP), PROFINET-compliant ring redundancy (MRP), redundancy manager integrated
- Quick and easy diagnostics with LEDs on the device, using integrated Web server and via SNMP
- Integration of SCALANCE XB-200 switches in the existing network management infrastructure, e.g. SINEMA Server, with SNMP access point
- Load limiting when using multicast-based protocols (Voice over IP, Video) thanks to IGMP Snooping/Querier and additional multicast and broadcast limiting per port
- Uncrossed connecting cables can be used due to the integrated auto crossover function
- Support of the two industrial protocols, PROFINET and Ethernet/IP, in the same device
- Low-maintenance operation due to fanless construction
- Support of VLANs permits integration into Enterprise Security Policies

Application

The unmanaged Industrial Ethernet switches of the SCALANCE XB-000 line allow cost-effective solutions for setting up small, electrical/optical star or line topologies with switching functionality in machines or plant units. The enclosure is designed for space-saving installation in a control cabinet on a standard rail.



Integration of the SIMATIC MV420 and MV440 into the automation network

The SCALANCE XB-200 Industrial Ethernet switches are simple, low-cost Industrial Ethernet switches that contain the necessary software functionalities for automation with various protocols. The devices with degree of protection IP20 are designed for operation in the control cabinet.



Connection of SIMATIC RF685R and RF680R to PROFINET

Industrial Wireless LAN SCALANCE W

Overview



With the SCALANCE product family, Siemens offers a wide range of Industrial Wireless LAN network components for industrial use. They can be used for all Ethernet-based SIMATIC Ident devices (e.g. MV400 optical readers, RF600 reader, RF180C communication module) to establish a wireless network architecture

Some of the IWLAN components recommended by Siemens are listed under the accessories for the SIMATIC Ident devices (e.g. SCALANCE W788-1 M12 for the SIMATIC RF650M handheld terminal (see page 3/41 in Catalog ID 10, 2016).

The SCALANCE W products provide a combination of reliability, ruggedness and security in a single product:

- · For use by industrial and automation customers
- For outdoor use under demanding climatic conditions
- For low-cost integration into the control cabinet or in devices

Mobile end devices (e.g. SIMATIC RF650M) allow for an uninterrupted flow of information from the enterprise level right through to the production level. This means that information can be provided quickly, reliably and easily at the right place and at the right time by wireless.

In this section, you can find an extract from the SCALANCE W-700 portfolio as a supplement.

You can find more information and the entire portfolio of SCALANCE W, cables, antennas and antenna accessories, with the associated order numbers, in Catalog IK PI.

Product versions

SCALANCE W788-1 M12

A radio card is permanently installed, functional scope can be expanded by using a KEY-PLUG W780 iFeatures.

SCALANCE W788-2 M12

Two radio cards are permanently installed, functional scope can be expanded by using a KEY-PLUG W780 iFeatures.

Benefits

Designed for Industry get

- · Predictable data traffic (deterministic response) and defined response times on the wireless link
- · Reliable wireless link, e.g. by using MIMO technology and monitoring the wireless link
- · Cost savings due to one single wireless network both for process-critical data and for non-critical communication
- Future-proof because all products are compatible with the internationally recognized WLAN standard IEEE 802.11n, suitable for license-free 2.4 GHz and 5 GHz frequency bands (ISM bands)
- Reduced operating costs since there is no wear and tear on rotating and moving plant sections
- Investment protection because flexible feature expansions (iFeatures) are possible using the KEY-PLUG

Application

The access points of the SCALANCE W700 product line are designed for both industrial use and for demanding climatic requirements outdoors.

Versions for the inexpensive integration into cabinets or machines are also available. They provide a reliable wireless link, redundancy mechanisms, and fast handover of nodes from one access point to the next (roaming). This allows processes to be monitored and loss of production due to machine downtimes to be avoided.

Industrial Wireless LAN (IWLAN) can also be used in time-critical applications in factory automation (PROFINET) or for safety-related signals (PROFIsafe).

SCALANCE W products are silicone-free and can therefore also be used in paint shops.



Mobile RFID data acquisition system, connected via SCALANCE W788-1 M12

Appendix



6/2	Training
6/3	Siemens Automation Cooperates with Education
6/5	Partners at Siemens Industry Automation and Drives Technologies
6/6	Online Services
6/8	Industry Services
6/12	Software licenses
6/14	Index
6/15	Article number index
6/18	Terms and conditions of sale and delivery

You benefit from practical training right from the manufacturer

SITRAIN Training for Industry provides you with comprehensive support in solving your tasks.

Training right from the manufacturer enables you to make better choices with more confidence in your decision-making processes.

SITRAIN Training means:

- Less time for commissioning, maintenance and servicing
- · Optimized production operations
- Safe engineering and commissioning
- Shorter start-up times, reduced downtimes and faster fault clearance
- · Swift elimination of deficits in existing plants
- Avoidance of costly planning errors right from the start
- Flexible plant adaptation to market requirements
- · Ensure quality standards in production
- · Increased employee satisfaction and motivation
- Shorter orientation periods in case of technology or personnel change



Contact

Visit our website at:

www.siemens.com/sitrain

or let us advise you personally. You can request our latest training catalog from:

SITRAIN – Training for Industry Customer Support Germany:

Phone: +49 911 895-7575

Fax: +49 911 895-7576

E-mail: info@sitrain.com



Important key data

Top trainers

Our trainers are skilled specialists with direct and extensive practical experience. Course developers have close contact with product development and directly pass on their knowledge to the trainers, and with that at the end to you.

Practical experience

Practice makes perfect – that's why we attach greatest importance to hands-on learning. Practical exercises can comprise up to half of the course time. You can therefore immediately implement your new knowledge in your day-to-day work.

300 courses in 62 countries

We offer a total of about 300 local attendance courses. You can find us at more than 50 locations in Germany, and in 62 countries worldwide. To find out which course is held at which location, go to:

www.siemens.com/sitrain

Customized training

Would you prefer individual training instead? Our solution: We will provide a program tailored exactly to your personal requirements. Training can be carried out in our Training Centers or onsite at your company.

We instruct you using state-of-the-art training equipment which has been especially designed by our developers for the SITRAIN courses. This training approach will give you all the assurance you need.

The right mixture: Blended learning

Blended learning involves a combination of various training media. For example, a face-to-face course in a training center can be optimally supplemented by teach-yourself Web-based training (WBT) courses as preparation or follow-up. The add-on effect: Reduced traveling costs and periods of absence.



Unique support for educators and students in educational institutions



Siemens Automation Cooperates with Education (SCE)

offers a global system for sustained support of technical skills. SCE supports educational institutions in their teaching assignment in the industrial automation sector and offers added value in the form of partnerships, technical expertise, and know-how. As the technological leader, our comprehensive range of services can support you in the knowledge transfer for Industry 4.0.

Our services at a glance

- Training curriculums for your lessons
- Trainer packages for hands-on learning
- Courses convey up-to-date specialist knowledge
- Support for your projects / textbooks
- · Complete didactic solutions from our partners
- Personal contact for individual support

Training curriculums for your lessons



Use our profound industrial know-how for practiceoriented and individual design of your course. We offer you more than 100 didactically prepared training curriculums on the topics of automation and drives technology free of charge. These materials are perfectly matched to your curricula and syllabuses, and optimally suited for use with our trainer packages. This takes into account all aspects of a modern industrial solution: installation, configuration, programming, and commissioning. All documents, including projects, can be individually matched to your specific requirements.

Particular Higghts:

 The new SIMATIC PCS 7 curriculums and trainer packages. Using plant simulation, you can pass on basic, practiceoriented PCS 7 knowledge at universities within about 60 hours (= 1 semester). • The new TIA Portal training materials for SIMATIC S7-1500 / S7-1200 / S7-300 are available in English, German, French, Italian, Spanish, Portuguese and Chinese for download.

www.siemens.com/sce/curriculums

Trainer packages for hands-on learning



Our SCE trainer packages offer a specific combination of original industrial components which are perfectly matched to your requirements and can be conveniently used in your course. These price-reduced bundles available exclusively to schools include innovative and flexible hardware and software packages.

SČE currently offers more than 80 SCE trainer packages including related equipment e.g. Micro Memory. These cover both the factory and process automation sectors. You can use them to impart the complete course contents on industrial automation at a very low cost.

Trainer packages are available for:

- Introduction to automation technology with LOGO! logic module
- PLC engineering with SIMATIC S7 hardware and STEP 7 software (S7-1500, S7-1200, S7-300 and TIA Portal)
- Operator control and monitoring with SIMATIC HMI
- Industrial networking over bus systems with SIMATIC NET (PROFINET, PROFIBUS, IO-Link)
- Sensor systems with VISION, RFID and SIWAREX
- Process automation with SIMATIC PCS 7
- Networked drive and motion technologies with SINAMICS/SIMOTION
- Power Monitoring Devices SENTRON PAC 4200
- Motor Management SIMOCODE
- CNC programming with SinuTrain

Important ordering notes:

Only the following institutions are authorized to obtain trainer packages: vocational schools, Colleges and Universities, in-house vocational training departments, non commercial research institutions and non commercial training departments.

To purchase a trainer package, you require a specific end-use certificate, which you can obtain from your regional sales office.

www.siemens.com/sce/tp

Appendix Siemens Automation Cooperates with Education

Simplify your education in automation

Unique support for educators and students in educational institutions (continued)

Courses convey up-to-date specialist knowledge



Profit from our excellent know-how as the leader in industrial technologies. We offer you specific courses for automation and drive technology worldwide. These support you in the practiceoriented transferring of product and system know-how, are in conformance with curriculums, and derived from the training fields. Compact technical courses especially for use at universities are also available.

Our range of courses comprises a wide variety of training modules based on the principle of Totally Integrated Automation (TIA). The focus is on the same subject areas as with the SCE trainer packages.

Every PLC and drive course is oriented on state-of-the-art technology. Your graduates can thus be prepared optimally for their future professional life.

In some countries we are offering classes based on our training curriculums. Please inquire with your SCE contact partner.

www.siemens.com/sce/courses



Automation and drive technology is characterized by continuous and rapid developments. Service and Support therefore play an important role.

As a particular service, SCE supports technical authors with our know-how as well as with intensive technical consulting. Siemens library of special textbooks covering the industrial automation sector provides an additional resource for you and your students. These can be found at the SCE web site.

www.siemens.com/sce/contact www.siemens.com/sce/books

Complete didactic solutions from our partners



Our partners for learning systems offer a wide range of training systems and solutions for use in your courses or laboratory.

These models have been designed based on our trainer packages and thus save you the time and cost of selfconstruction of individual components. The Partner systems provide you with simple and effective help in the fulfillment of your teaching assignment.

www.siemens.com/sce/partner

Contact for individual support

You can find your personal SCE contact on our Internet site. Your local SCE Promoter will answer all your questions concerning the complete SCE offering, and provide you with timely and competent information about innovations. When you encounter challenges, you can profit from our global team of excellence.

If a direct SCE contact is not listed for your country, please contact your local Siemens office.

www.siemens.com/sce/contact

SCE Support Finder for your Internet request

You are an educator and need support on the topic of industry automation? Send us your request:

www.siemens.com/sce/supportfinder

Discover SCE





semena sem Bobel Metale I & Semena AD 1985-2014 | Corporate Information | Privacy Policy | Terms of Use | Digital D

At Siemens we are resolutely pursuing the same goal: long-term improvement of your competitive ability. We are committed to this goal. Thanks to our commitment,

We are committed to this goal. Thanks to our commitment, we continue to set new standards in automation and drive technology. In all industries – worldwide.

At your service locally, around the globe for consulting, sales, training, service, support, spare parts ... on the entire Industry Automation and Drive Technologies range.

Your personal contact can be found in our Contacts Database at: www.siemens.com/automation/partner

You start by selecting

- the required competence,
- products and branches,
- a country,
- a city
- or by a
- location search or
- person search.



						🚯 All about industry
	Feeley			× 🕀 Location search		× search
quantitized	By Competence	* *	# products and ibranches	r Infand	v x Ouble	v x Coural Mon
Sement 14. Sement		Lease Oran 2 Dame Interest	Communities Bin Hard (Section 1) Bin Hard			A Property Service of the service of

Appendix

Online Services

Information and Ordering Options on the Internet and DVD

The Future of Manufacturing on the Internet



Detailed knowledge of the range of products and services available is essential when planning and engineering automation systems. It goes without saying that this information must always be as up-to-date as possible.

Industry is on the threshold of the fourth industrial revolution as digitization now follows after the automation of production. The goals are to increase productivity and efficiency, speed, and quality. In this way, companies can remain competitive on the path to the future of industry.

You will find everything you need to know about products, systems and services on the internet at:

www.siemens.com/industry

Product Selection Using the Interactive CA 01 Automation and Drives Catalog



Easy Shopping with the Industry Mall



Detailed information together with user-friendly interactive functions:

The CA 01 interactive catalog covers more than 100,000 products, thus providing a comprehensive overview of the product range provided by Siemens.

You will find everything you need here for solving tasks in the fields of automation, switching, installation and drives. All information is provided over a user interface that is both user-friendly and intuitive.

You can order the CA 01 product catalog from your Siemens sales contact or in the Information and Download Center:

www.siemens.com/industry/infocenter

Information about the CA 01 interactive catalog can be found on the Internet at:

www.siemens.com/automation/ca01

or on DVD.

The Industry Mall is the electronic ordering platform of Siemens AG on the Internet. Here you have online access to a huge range of products presented in an informative and attractive way.

Data transfer via EDIFACT allows the whole procedure, from selection through ordering to tracking and tracing, to be carried out online. Availability checks, customer-specific discounts and bid creation are also possible.

Numerous additional functions are provided for your support. For example, powerful search functions make it easy to select the required products. Configurators enable you to configure complex product and system components quickly and easily. CAx data types are also provided here.

You can find the Industry Mall on the Internet at:

www.siemens.com/industrymall

Information and Download Center, Social Media, Mobile Media

Downloading Catalogs



In addition to numerous other useful documents, you can also find the catalogs listed on the back inside cover of this catalog in the Information and Download Center. You can download these catalogs in PDF format without having to register.

The filter dialog above the first catalog displayed makes it possible to carry out targeted searches. If you enter "MD 3" for example, you will find both the MD 30.1 and MD 31.1 catalogs. If you enter "IC 10", both the IC 10 catalog and the associated news or add-ons are displayed.

Visit us at:

www.siemens.com/industry/infocenter

Social and Mobile Media



Connect with Siemens through social media: visit our social networking sites for a wealth of useful information, demos on products and services, the opportunity to provide feedback, to exchange information and ideas with customers and other Siemens employees, and much, much more. Stay in the know and follow us on the ever-expanding global network of social media.

To find out more about Siemens' current social media activities, visit us at:

www.siemens.com/socialmedia

Or via our product pages at:

www.siemens.com/automation or www.siemens.com/drives

Connect with Siemens Industry at our central access point to read all the news on the future of manufacturing, watch current videos and inform yourself about all the latest industry developments:

www.siemens.com/future-of-manufacturing/news.html

Discover the world of Siemens.

We are also constantly expanding our offering of cross-platform apps for smartphones and tablets. You will find the current Siemens apps at the App Store (iOS) or at Google Play (Android):

https://itunes.apple.com/en/app/siemens/id452698392?mt=8

https://play.google.com/store/search?q=siemens

The Siemens app, for example, tells you all about the history, latest developments and future plans of the company – with informative pictures, fascinating reports and the most recent press releases.

Appendix

Industry Services

Overview

Unleash potential – with services from Siemens



Increase your performance – with Industry Services

Optimizing the productivity of your equipment and operations can be a challenge, especially with constantly changing market conditions. Working with our service experts makes it easier. We understand your industry's unique processes and provide the services needed so that you can better achieve your business goals.

You can count on us to maximize your uptime and minimize your downtime, increasing your operations' productivity and reliability. When your operations have to be changed quickly to meet a new demand or business opportunity, our services give you the flexibility to adapt. Of course, we take care that your production is protected against cyber threats. We assist in keeping your operations as energy and resource efficient as possible and reducing your total cost of ownership. As a trendsetter, we ensure that you can capitalize on the opportunities of digitalization and by applying data analytics to enhance decision making: You can be sure that your plant reaches its full potential and retains this over the longer lifespan.

You can rely on our highly dedicated team of engineers, technicians and specialists to deliver the services you need - safely, professionally and in compliance with all regulations. We are there for you, where you need us, when you need us.

Overview



Make your industrial processes transparent to gain improvements in productivity, asset availability, and energy efficiency.

Production data is generated, filtered and translated with intelligent analytics to enhance decision-making.

This is done whilst taking data security into consideration and with continuous protection against cyber attack threats.

www.industry.siemens.com/services/global/en/portfolio/ plant-data-services/Pages/index.aspx



Industry Online Support site for comprehensive information, application examples, FAQs and support requests.

Technical and Engineering Support for advice and answers for all inquiries about functionality, handling, and fault clearance.

Information & Consulting Services, e.g. SIMATIC System Audit; clarity about the state and service capability of your automation system or Lifecycle Information Services; transparency on the lifecycle of the products in your plants.

www.industry.siemens.com/services/global/en/portfolio/ support-consulting/Pages/index.aspx



From the basics and advanced to specialist skills, SITRAIN courses provide expertise right from the manufacturer – and encompass the entire spectrum of Siemens products and systems for the industry.

Worldwide, SITRAIN courses are available wherever you need a training course in more than 170 locations in over 60 countries.

www.industry.siemens.com/services/global/en/portfolio/ training/Pages/index.aspx



Are available worldwide for smooth and fast supply of spare parts – and thus optimal plant availability. Genuine spare parts are available for up to ten years. Logistic experts take care of procurement, transport, custom clearance, storage and order management. Reliable logistics processes ensure that components reach their destination as needed.

Asset optimization services help you design a strategy for parts supply where your investment and carrying costs are reduced and the risk of obsolescence is avoided.

www.industry.siemens.com/services/global/en/portfolio/ spare_parts/Pages/index.aspx

Appendix

Industry Services

Industry Services – Portfolio overview

Overview (continued)



Are offered on-site and in regional repair centers for fast restoration of faulty devices' functionality.

Also available are extended repair services, which include additional diagnostic and repair measures, as well as emergency services.

www.industry.siemens.com/services/global/en/portfolio/ repair_services/Pages/index.aspx



Provide a cost-effective solution for the expansion of entire plants, optimization of systems or upgrading existing products to the latest technology and software, e.g. migration services for automation systems.

Service experts support projects from planning through commissioning and, if desired over the entire extended lifespan, e.g. Retrofit for Integrated Drive Systems for an extended lifetime of your machines and plants

www.industry.siemens.com/services/global/en/portfolio/ retrofit-modernization/Pages/index.aspx



Siemens specialists are available globally to provide expert field and maintenance services, including commissioning, functional testing, preventive maintenance and fault clearance. All services can be included in customized service agreements with defined reaction times or fixed maintenance intervals.

www.industry.siemens.com/services/global/en/portfolio/ field_service/Pages/index.aspx



A technical Service Program or Agreement enables you to easily bundle a wide range of services into a single annual or multiyear agreement.

You pick the services you need to match your unique requirements or fill gaps in your organization's maintenance capabilities.

Programs and agreements can be customized as KPI-based and/or performance-based contracts.

www.industry.siemens.com/services/global/en/portfolio/ service_programs/Pages/index.aspx

Online Support

Overview



Online Support is a comprehensive information system for all questions relating to products, systems, and solutions that Siemens has developed for industry over time. With more than 300,000 documents, examples and tools, it offers users of automation and drive technology a way to quickly find up-to-date information. The 24-hour service enables direct, central access to detailed product information as well as numerous solution examples for programming, configuration and application.

The content, in six languages, is increasingly multimedia-based – and now also available as a mobile app. Online support's "Technical Forum" offers users the opportunity to share information with each other. The "Support Request" option can be used to contact Siemens' technical support experts. The latest content, software updates, and news via newsletters and Twitter ensure that industry users are always up to date.

www.siemens.com/industry/onlinesupport

Online Support App



Using the Online Support app, you can access over 300,000 documents covering all Siemens industrial products – anywhere, any time. Regardless of whether you need help implementing your project, fault-finding, expanding your system or are planning a new machine.

You have access to FAQs, manuals, certificates, characteristic curves, application examples, product notices (e.g. announcements of new products) and information on successor products in the event that a product is discontinued.

Just scan the product code printed on the product directly using the camera of your mobile device to immediately see all technical information available on this product at a glance. The graphical CAx information (3D model, circuit diagrams or EPLAN macros) is also displayed. You can forward this information to your workplace using the e-mail function.

The search function retrieves product information and articles and supports you with a personalized suggestion list. You can find your favorite pages – articles you need frequently – under "mySupport". You also receive selected news on new functions, important articles or events in the News section. Scan the QR code for information on our Online Support app.



The app is available free of charge from the Apple App Store (iOS) or from Google Play (Android).

https://support.industry.siemens.com/cs/ww/en/sc/2067

Software Licenses

Overview

Software types

Software requiring a license is categorized into types. The following software types have been defined:

- Engineering software
- Runtime software

Engineering software

This includes all software products for creating (engineering) user software, e.g. for configuring, programming, parameterizing, testing, commissioning or servicing.

Data generated with engineering software and executable programs can be duplicated for your own use or for use by thirdparties free-of-charge.

Runtime software

This includes all software products required for plant/machine operation, e.g. operating system, basic system, system expansions. drivers. etc.

The duplication of the runtime software and executable programs created with the runtime software for your own use or for use by third-parties is subject to a charge.

You can find information about license fees according to use in the ordering data (e.g. in the catalog). Examples of categories of use include per CPU, per installation, per channel, per instance, per axis, per control loop, per variable, etc.

Information about extended rights of use for parameterization/configuration tools supplied as integral components of the scope of delivery can be found in the readme file supplied with the relevant product(s).

License types

Siemens Industry Automation & Drive Technologies offers various types of software license:

- Floating license
- Single license
- Rental license
- Rental floating license
- Trial license
- Demo license
- Demo floating license

Floating license

The software may be installed for internal use on any number of devices by the licensee. Only the concurrent user is licensed. The concurrent user is the person using the program. Use begins when the software is started. A license is required for each concurrent user.

Single license

Unlike the floating license, a single license permits only one installation of the software per license.

The type of use licensed is specified in the ordering data and in the Certificate of License (CoL). Types of use include for example per instance, per axis, per channel, etc.

One single license is required for each type of use defined.

Rental license

A rental license supports the "sporadic use" of engineering software. Once the license key has been installed, the software can be used for a specific period of time (the operating hours do not have to be consecutive).

One license is required for each installation of the software.

Rental floating license

The rental floating license corresponds to the rental license, except that a license is not required for each installation of the software. Rather, one license is required per object (for example, user or device).

Trial license

A trial license supports "short-term use" of the software in a nonproductive context, e.g. for testing and evaluation purposes. It can be transferred to another license.

Demo license

The demo license support the "sporadic use" of engineering software in a non-productive context, for example, use for testing and evaluation purposes. It can be transferred to another license. After the installation of the license key, the software can be operated for a specific period of time, whereby usage can be interrupted as often as required.

One license is required per installation of the software.

Demo floating license

The demo floating license corresponds to the demo license, except that a license is not required for each installation of the software. Rather, one license is required per object (for example, user or device).

Certificate of license (CoL)

The CoL is the licensee's proof that the use of the software has been licensed by Siemens. A CoL is required for every type of use and must be kept in a safe place.

Downaradina

The licensee is permitted to use the software or an earlier version/release of the software, provided that the licensee owns such a version/release and its use is technically feasible.

Deliverv versions

Software is constantly being updated. The following delivery versions

- PowerPack
- Upgrade

can be used to access updates.

Existing bug fixes are supplied with the ServicePack version.

PowerPack

PowerPacks can be used to upgrade to more powerful software. The licensee receives a new license agreement and CoL (Certificate of License) with the PowerPack. This CoL, together with the CoL for the original product, proves that the new software is licensed.

A separate PowerPack must be purchased for each original license of the software to be replaced.

Appendix

Overview

Uprgade

An upgrade permits the use of a new version of the software on the condition that a license for a previous version of the product is already held.

The licensee receives a new license agreement and CoL with the upgrade. This CoL, together with the CoL for the previous product, proves that the new version is licensed.

A separate upgrade must be purchased for each original license of the software to be upgraded.

ServicePack

ServicePacks are used to debug existing products.

ServicePacks may be duplicated for use as prescribed according to the number of existing original licenses.

License key

Siemens Industry Automation & Drive Technologies supplies software products with and without license keys.

The license key serves as an electronic license stamp and is also the "switch" for activating the software (floating license, rental license, etc.).

The complete installation of software products requiring license keys includes the program to be licensed (the software) and the license key (which represents the license).

Software Update Service (SUS)

As part of the SUS contract, all software updates for the respective product are made available to you free of charge for a period of one year from the invoice date. The contract will automatically be extended for one year if it is not canceled three months before it expires.

The possession of the current version of the respective software is a basic condition for entering into an SUS contract.

You can download explanations concerning license conditions from www.siemens.com/automation/salesmaterial-as/catalog/en/terms_of_trade_en.pdf

Appendix Index

Deute and at Ciana and Industry	
Partners at Siemens Industry	6/5
Antennas	
ANT 1	2/131
ANT 12	2/136
ANT 18	2/137
ANT 2 2/122	2/10/
ANT 3	2/133
ANT 30	2/138
ANT 8	2/134
ANT D1	2/139
ANT D10	2/145
ANT D2	2/140
ANT D5	2/141
ANT D6	2/143
BE620A	3/45
DE640A	2/10
DEC40A	0/40
RF042A	3/48
RF660A	3/51
Antenna multiplexer 2/99, 2/141, 2/143,	2/146
Antenna switch	2/146
Asset Management	1/4
	, .
С	
CA 01interactive catalog	6/6
Code readers	4/2
Communication modules	
	E / A
A ONA 475	3/4
ASM 475	5/22
RF120C	5/19
RF160C	5/4
RF170C	. 5/16
RF180C	5/9
RFID181EIP	
BE182C	5/9
	0/100
Configuring instructions for MOBY D	2/129
Container transponder SIMATIC RF6201	3/16
D	0/10
D Digital Enterorise	1/7
D Digital Enterprise	1/7
D Digital Enterprise Direct part marking	1/7 4/2
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T	1/7 4/2 3/20
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T	1/7 4/2 3/20
Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T	1/7 4/2 3/20
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems	1/7 4/2 3/20 4/37
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320	1/7 4/2 3/20 4/37 4/39
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325	1/7 4/2 3/20 4/37 4/39 4/41
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340	1/7 4/2 3/20 4/37 4/39 4/41 4/43
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M	1/7 4/2 3/20 4/37 4/39 4/41 4/43 2/82
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M	1/7 4/2 3/20 4/37 4/39 4/41 4/43 2/82
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal DESCM	1/7 4/2 3/20 4/37 4/39 4/41 4/43 2/82
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M	1/7 4/2 3/20 4/37 4/39 4/39 4/41 4/43 2/82 2/117
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Hadheld reading systems. MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M	1/7 4/2 3/20 4/37 4/39 4/39 4/41 4/43 2/82 2/117 3/42
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF530M RF650M MOBY D	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV322	1/7 4/2 3/20 4/37 4/39 4/39 4/41 4/43 2/82 2/117 3/42 2/120 4/39 4/41
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320 MV320 MV320 MV340	1/7 4/3 4/37 4/37 4/37 4/31 4/43 2/117 2/120 4/41 4/43
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF550M MV320 MV320 Handheld terminal RF350M RF650M MOBY D MV325 MV340 Heat-resistant transponder	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV325 MV326 MV340 Restown RF650M MOBY D MV340 Heat-resistant transponder MDS D 124	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV325 MV320 MV320 MV320 MV324 MDS D 124 MDS D 124 MDS D 139	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems. MV320 MV325 MV340 RF210M Handheld terminal RF650M MOBY D MV320. MV320. MV320. MDS D 124. MDS D 129. MDS D 140.	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320 MV320 MV320 MV320 MV325 MV340 RF650M MOBY D MV320 MV320 MV340 Heat-resistant transponder MDS D124 MDS D139 MDS D139	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320 MV325 MV320 MDS D MV340 Heat-resistant transponder MDS D124 MDS D139 MDS D160 MDS D339	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320 MV320 MV320 MV320 MV320 MDS D 124 MDS D 139 MDS D 139 MDS D 339 RF380T	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems. MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320. MV320. MV320. MDS D MDS D124. MDS D139. MDS D139. RF380T RF680L	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320 MV320 MV320 MV321 MV320 MV320 MV320 MV321 MDS D MDS D124 MDS D139 MDS D160 MDS D339 RF380T RF630L	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320 MV325 MV340 REstown MOBY D MV325 MV340 Heat-resistant transponder MDS D124 MDS D139 MDS D139 RF680L RF680L RF690L RF680T	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320 MV320 MV320 MV325 MV340 Heat-resistant transponder MDS D124 MDS D139 MDS D160 MDS D339 RF680L RF680L RF680L RF680L	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320 MV320 MV320 RF650M MOBY D MV320 MV320 MV320 MDS D124 MDS D124 MDS D139 MDS D139 RF680L RF680L RF680L RF680L RF680L	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems. MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320 MV320 MV320 MDS D MDS D124 MDS D124 MDS D124 MDS D139 RF680L RF680L RF680L RF680L RF680L RF680L RF680T I Industry Services	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320 MV320 MV320 MV320 MV325 MV340 RF650M MOBY D MV320 MV320 MV320 MV321 MV320 MV320 MV320 MDS D124 MDS D124 MDS D139 MDS D139 RF380T RF680L RF680L RF680L RF680T I Industry Services IO-L ink	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320 MV320 MV320 MV320 MV320 MV320 MV340 Heat-resistant transponder MDS D124 MDS D139 MDS D160 MDS D339. RF680L	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems MV320 MV325 MV340 RF210M Handheld terminal RF350M RF650M MOBY D MV320 MV340 Heat-resistant transponder MDS D124 MDS D139 MDS D139 MDS D339 RF680L RF680L <td></td>	
D Digital Enterprise Direct part marking Disk transponder SIMATIC RF625T H Handheld reading systems. MV320. MV325. MV340. RF210M. Handheld terminal RF350M. RF650M. MOBY D. MV320. MV340. Heat-resistant transponder MDS D124. MDS D139. MDS D160. MDS D139. RF6801. RF6802. RF6801. RF6802. RF6803. MOL	

L
Large memory label RF622L
Large memory transponder RF622T3/18
Lenses
Long range reader RF290R2/99
M
Mall 6/6
MOBY D 2/120
0
Object recognition4/54
OCR
Un-metal labels
RF04UL
Ontical readers 4/37
MV320 4/39
MV3254/41
MV3404/43
P
Pat-Genius 1/54
Production control 1/4
R
Readers
RF210M
RF210R2/79 RF220R 2/83
BE240B 2/86
RF250R
RF260R2/95
RF290R2/99
RF310R2/105
RF340R2/107
RF350M2/117
RF350R
BE382B
RF650M
RF650R3/30
RF680R3/33
RF685R
SLG D11/SLG D1152/123
SLG D12/D1252/120 PE200 2/76
RE300 2/102
BE600 3/1
BEID standard cables 5/25
BEID systems for the HE range 2/1
BEID systems for the UHE range 3/1
5
SCALANCE network components
X108PoF 4/29
XB205-3
X204IRT PRO
Scanmode readers
RF310R2/105
RF380R2/112
RF382R
Screw transponder SIMATIC RF6301
Education (SCE)
SIMATIC Ident
SITRAIN – Training for Industry
Skid identification
SmartLabels
MDS D1652/8
MDS D2612/8
RF622L3/5

RF640L	
PEGON	2/11
	3/11
RF690L	3/12
Social and Mobile Media	6/7
Software Licenses	6/12
Survivale Licenses	0/12
Stationary code reading systems	4/6
MV420	4/11
MV440	4/20
Quere la Obrie Management	
Supply Chain Management	1/5
τ	
1	
Terms and conditions	
of sale and delivery	6/18
Text-Genius	4/50
	4/30
Third-party systems	1/6
Tool transponder SIMATIC RF640T	3/24
Totally Integrated Automation	1/6
Totally Integrated Automation	1/0
Tracking & Tracing	1/5
Transponders	
	2/10
	2/10
MDS D117	2/44
MDS D124	2/26
MDS D126	2/38
MDS D127	2/46
MD0 D127	2/40
MDS D139	2/52
MDS D160	2/56
MDS D165	2/8
	2/12
MD0 D200	2/ 12
MDS D261	2/8
MDS D324	2/28
MDS D339	2/54
MDS D400	2/14
	0/10
WDS D421	2/10
MDS D422	2/20
MDS D423	2/24
MDS D424	2/30
	2/24
MD3 D423	2/34
MDS D426	2/40
MDS D428	2/48
MDS D460	2/58
MDS D521	2/18
MD0 D521	2/10
MDS D522	2/22
MDS D524	2/32
MDS D525	2/36
MDS D526	2/42
MDC DE20	0/50
IVIDS D528	2/50
RF3201	2/61
RF330T	2/63
BE340T	2/65
DE250T	2/67
DE000T	2/07
RF3601	2/69
RF370T	2/71
RF380T	2/73
BE610T	3/14
PECOOT	2/16
	3/10
RF622L	3/5
RF622T	3/18
RF625T	3/20
BE630I	3/6
DECODE	0,0
	3/22
RF64UL	3/9
RF640T	3/24
RF680L	3/11
BE680T	3/26
REGON	2/10
	J/ 12
V	
verification systems	4/45
Veri-Genius	4/45
W	
Web-based interface for	
RF600 reader	3/29

© Siemens AG 2016

Appendix Article number index

3RX9
3RX9802-0AA00
6557
6ES7127 6BD00 0BA0 2/81 2/85 2/88
2/93, 2/97
6ES7138-4GA50-0AB0
6ES7147-5JD00-0BA0 2/81, 2/85, 2/88,
6ES7148-6JA00-0AB02/81, 2/85, 2/88, 2/03, 2/03
6ES7194-34400-0440 5/7
6ES7194 3AA00 0BA0
6ES7194-3 A00-06A0 5/8 5/14
6ES7194-4 450-0440
6ES7194 4 ID50 0000 5/14
6ES7278 4RD22 0VR0 2/81 2/85 2/88
2/93, 2/97
6ES7390-5AA00-0AA05/24
6ES7390-5BA00-0AA05/24
6ES7392-1AJ00-0AA05/24
6ES7392-1BJ00-0AA0
6053
6GF3020-0AC40-0AC1
6GF3020-0AC40-0AC3
6GF3020-0AC40-0AC4
6GF3020-0AC40-0AC5
6GF3020-0AC40-0AC7
6GF3020-0AC40-0AC8
6CE3020 0AC40 0AP2
6GE3320-0AC02
6GE3320-0AC03 4/40
6GE3320-0AC07 4/40
6GF3320-0HT01
6GF3325-0AC03
6GF3325-0AC07
6GF3325-0HT01 4/42
6GF3340-0HT01 4/44
6GF3400-0BH154/18, 4/29
6GF3400-0LT01-7BA1 4/28
6GF3400-0LT01-8DA1 4/28
6GF3400-0SL01
6GF3400-0SL02
6GF3400-0SL03
6GF3400-1BH20
6GF3400-1SL01
6GF3420-0AA20 4/17
6GF3420-0AA40
6GF3420-0AC00-0LK0 4/17
6GF3420-0AC00-1AA04/18
6GF3420-0AC00-1LK0 4/17
6GF3420-0AC00-1LT0
6GF3420-0AC00-1PS0 4/18
6GF3420-0AC00-2AA0
6GF3420-0AC00-2CB0
6GF3420-0AC00-2L10
0GF342U-UAUUU-3LIU
6GE3420-0AX40 4/17
6GE3440.1CD10 4/27
6GE3440-1GE10 4/27
6GE3440-11 E10 //27
6GF3440-8AC11 4/27
6GF3440-8AC12. 4/27
6GF3440-8AC13
6GF3440-8AC21
6GF3440-8BA2

6GF3440-8BA44/18, 4/29
6GF3440-8BC44/29
6GF3440-8BD14/29
6GF3440-8CA4/29
6GF3440-8CD01
6GF3440-8CE4/49
6GE3440-8DA11 4/28
6GF3440-8DA21 4/28
CCF3440-0DA314/20
6GF3440-6DA41
6GF3440-8EA14/34
6GF9
6GE9001-1AP02 4/33
6GF9001_1BB01 4/33
6GE9001-1BE01
00F0001 1DE01
6GF9001-1BF014/33
6GF9001-1BG014/33
6GF9001-1BH014/33
6GF9001-1BJ014/33
6GF9001-1BK014/33
6GF9001-1BL014/33
6GF9001-1BU4/34
6GE9001-1BU01 4/34
6GE9001-1BV 4/34
6CE0001 24D
00F0001 0AF
6GF9001-2AE4/34
6GF9001-2AF4/34
6GF9002-7AD4/29
6GK1
6GK1901-0DB20-6440 5/14
CCK1001 0DM20 0AAF
6GK 1901-0DM20-2AA5
6GK1901-1BB10-2AA04/17, 4/28, 5/14
6GK1901-1BB10-6AA05/14
6GK1905-0CA005/7
6GK1905-0CB005/7
6GK1905-0DA105/7
6GK1905-0EA00
6GK1905-0EB00
6GK1905-0EC00 5/7
6GK1905-0EA00 5/8 5/14
0GK 1903-0FB00
6GK 1907-0AB 10-6AAU5/14
6GK1907-0DB10-6AA35/26
6GK5
6GK5108-0PA00-2AA3 4/29
6GK5204-0 IA00-2BA6 5/14
CONFERENCE OF THE CONFERENCE O
······································
001\3790-0ME00-0AD32/101
6GT2
6GT2 6GT2002-0ED00
6GT2 6GT2002-0ED00
6GT2 6GT2002-0ED00 5/7 6GT2002-0EF00 5/7 6GT2002-0EF00 5/7
6GT2 6GT2002-0ED00 5/7 6GT2002-0EF00 5/7 6GT2002-0EF00 5/2 6GT2002-0GA10 5/24
6GT2 6GT2002-0ED00 5/7 6GT2002-0ED00 5/7 6GT2002-0EF00 5/7 6GT2002-0EF00 5/2 6GT2002-0EF00 5/24 6GT2002-0HD01 5/18
6GT2 6GT2002-0ED00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/2 6GT2002-0HD01 .5/24 6GT2002-0HD01 .5/18 6GT2002-0JD00 .5/13
6GT2 6GT2002-0ED00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/2 6GT2002-0HD01 .5/24 6GT2002-0HD01 .5/18 6GT2002-0JD00 .5/13 6GT2002-0JD10 .5/13
6GT2 6GT2002-0ED00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/24 6GT2002-0HD01 .5/24 6GT2002-0HD01 .5/18 6GT2002-0JD00 .5/13 6GT2002-0JD10 .5/13 6GT2002-0JD20 .5/13
6GT2 6GT2002-0ED00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0JD10 .5/18 6GT2002-0JD00 .5/13 6GT2002-0JD10 .5/13 6GT2002-0JD20 .5/13 6GT2002-0JA00 .5/20
6GT2 6GT2002-0ED00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0JD10 .5/18 6GT2002-0JD00 .5/13 6GT2002-0JD10 .5/13 6GT2002-0JD20 .5/13 6GT2002-0JD20 .5/13 6GT2002-0LA00 .5/20 6GT2002-1HD01 .5/18
6GT2 6GT2002-0ED00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0JD01 .5/18 6GT2002-0JD00 .5/13 6GT2002-0JD10 .5/13 6GT2002-0JD20 .5/13 6GT2002-0JD20 .5/13 6GT2002-0LA00 .5/20 6GT2002-1HD01 .5/18 6GT2002-1JD00 .5/13
6GT2 6GT2002-0ED00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0JD01 .5/18 6GT2002-0JD00 .5/13 6GT2002-0JD10 .5/13 6GT2002-0JD20 .5/13 6GT2002-0JD20 .5/13 6GT2002-1HD01 .5/18 6GT2002-1JD00 .5/13 6GT2002-2JD00 .5/13
6GT2 5/7 6GT2002-0ED00 5/7 6GT2002-0EF00 5/7 6GT2002-0EF00 5/24 6GT2002-0HD01 5/18 6GT2002-0JD10 5/13 6GT2002-0JD10 5/13 6GT2002-0JD10 5/13 6GT2002-0JD20 5/13 6GT2002-1HD01 5/18 6GT2002-1JD00 5/13 6GT2002-1JD00 5/13 6GT2002-1JD00 5/13 6GT2002-2JD00 5/13
6GT2 6GT2002-0ED00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0JD01 .5/13 6GT2002-0JD00 .5/13 6GT2002-0JD10 .5/13 6GT2002-0JD20 .5/13 6GT2002-0LA00 .5/20 6GT2002-1HD01 .5/13 6GT2002-2JD00 .5/13 6GT2002-2JD00 .5/13 6GT2002-2JD00 .5/13 6GT2002-2JD00 .5/13 6GT2002-2JD00 .5/13 6GT2002-2JD00 .5/13
6GT2 6GT2002-0ED00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0JD01 .5/18 6GT2002-0JD00 .5/13 6GT2002-0JD10 .5/13 6GT2002-0JD20 .5/13 6GT2002-0LA00 .5/20 6GT2002-1HD01 .5/18 6GT2002-1JD00 .5/13 6GT2002-2JD00 .5/13 6GT2080-2AA20 .2/81, 2/85, 2/88, 2/94,
6GT2 6GT2002-0ED00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0JD01 .5/18 6GT2002-0JD00 .5/13 6GT2002-0JD10 .5/13 6GT2002-0JD20 .5/13 6GT2002-0JD20 .5/13 6GT2002-1JD00 .5/13 6GT2002-1JD00 .5/13 6GT2002-2JD00 .5/13 6GT2002-4JD00 .5/13 6GT2080-2AA20 .2/81, 2/85, 2/88, 2/94,
6GT2 6GT2002-0ED00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0JD01 .5/18 6GT2002-0JD00 .5/13 6GT2002-0JD10 .5/13 6GT2002-0JD20 .5/13 6GT2002-0JD20 .5/13 6GT2002-0LA00 .5/20 6GT2002-1JD00 .5/13 6GT2002-2JD00 .5/13 6GT2002-2JD00 .5/13 6GT2002-4JD00 .5/13 6GT2002-4JD00 .2/81, 2/85, 2/88, 2/94,
6GT2 6GT2002-0ED00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0JD00 .5/13 6GT2002-0JD10 .5/13 6GT2002-0JD20 .5/13 6GT2002-0JD20 .5/13 6GT2002-0JD20 .5/13 6GT2002-1JD00 .5/13 6GT2002-1JD00 .5/13 6GT2002-2JD00 .5/13 6GT2002-2JD00 .5/13 6GT2002-2JD00 .5/13 6GT2002-2JD00 .5/13 6GT2002-2JD00 .5/13 6GT2002-2JD00 .2/81, 2/85, 2/88, 2/94,
6GT2 6GT2002-0ED00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0EF00 .5/7 6GT2002-0JD01 .5/13 6GT2002-0JD00 .5/13 6GT2002-0JD10 .5/13 6GT2002-0JD20 .5/13 6GT2002-0JD20 .5/13 6GT2002-1JD00 .5/13 6GT2002-1JD00 .5/13 6GT2002-2JD00 .5/13 6GT2002-4JD00 .5/13 6GT2002-4JD00 .5/13 6GT2080-2AA20 .2/81, 2/85, 2/88, 2/94,

6GT2090-0BE00
6GT2090-0QA00
6GT2090-0QB00 2/74
6GT2090-0VB00 5/8 5/15
6GT2090-4AN50 5/26
CT2000 4AT12 E/26
CCT2000 4AT90
6G12090-4A180
6G12091-4LH20 5/20, 5/26
6GT2091-4LH50 5/20, 5/26
6GT2091-4LN10 5/20, 5/26
6GT2190-0AA00 2/11, 2/13, 2/15, 2/70, 3/15
6GT2190-0AB00 2/11, 2/13, 2/15, 2/70, 3/15
6GT2390-0AA00 2/11, 2/13, 2/15
6GT2390-1AB00
6GT2391-0AH30 2/119 2/132 2/133 2/135
6GT2398-1CA00 2/93 2/110 2/119 2/137
6GT2398-1CB00 2/110 2/131
CT2308 10000 2/02 2/110 2/110 2/126
CCT2398-1CC00
0G12398-1CD00
6G12398-1CD30-0AX02/119, 2/132
6GT2398-1CD40-0AX0
6GT2398-1CD50-0AX0 2/119, 2/133
6GT2398-1CD60-0AX0 2/93, 2/110, 2/133
6GT2398-1CF00 2/119, 2/135
6GT2398-1CF10
6GT2490-1AA00
6GT2491-1HH50 2/125 2/127
6GT2491_4FH50 5/24 5/26
6CT2401 4EN20 5/24 5/26
COT0401 4ENE0
0G12491-4EIN30
6G12590-0QA00
6GT2600-0AA10
6GT2600-0AB10
6GT2600-0AC102/27
6GT2600-0AD102/11
6GT2600-0AE00
6GT2600-0AF00
6GT2600-0AG002/45
6GT2600-1AA01-0AX0
6GT2600-1AB00-0AX0 2/9
6GT2600-1AD00-0AX0 2/13
6GT2600-34410 2/55
CT2600 3AC00
CCT2C00-3AC00
0012000-4AA00
6G12600-4AB00
6GI2600-4AC002/31
6GT2600-4AD002/15
6GT2600-4AE00
6GT2600-4AF00 2/21
6GT2600-4AG002/35
6GT2600-4AH00
6GT2600-4AK00-0AX0
6GT2600-5AC00
6GT2600-5AE00 2/19
6GT2600-5AE00 2/23
6GT2600 5AE00 0AY0 2/23
CCT2000 EAU00
2/43
0G120UU-5AKUU2/51
6G12601-0AB00
6GT2602-0AB00
6GT2602-0AB10-0AX0
6GT2690-0AA00
6GT2690-0AC002/101, 2/141, 2/143
6GT2690-0AD002/101, 2/143
6GT2690-0AE00
6GT2690-0AG00
6GT2690-0AH00

6GT2690-0AH10	
6GT2690-0AK00	2/27 2/29 2/31 2/33
6GT2690-0AL00	
6GT2691-0CH33	
6GT2691-0CN10	
6GT2691-0DH72	2/139, 2/141, 2/143, 2/146
6GT2691-4BH50	
6GT2691-4BN20	
6GT2691-4FH20	. 5/8, 5/15, 5/18, 5/20, 5/26
6GT2698-1AC00	
6GT2698-2AC00	
6GT2698-5AA10	
6GT2698-5AB00	
6GT2698-5AC00	
6GT2698-5AF00	
6GT2698-5BB00	
6GT2800-1CA00	
6GT2800-4AC00	
6GT2800-4BB00	
6GT2800-5AC00	
6GT2800-5BA00	
6GT2800-5BB00	
6GT2800-5BD00	
6GT2800-5BE00	
6GT2800-5DA00	
6GT2800-6BE00	
6GT2801-1AB10	
6GT2801-1AB20-0AX	1 2/106
6GT2801-2AB10	
6GT2801-3AB10	
6GT2801-3AB20-0AX	0 2/82
6GT2801-3AB20-0AX	1 2/114
6GT2801-4AB10	
6GT2803-0BM00	
6GT2803-0CA00	
6GT2803-1BA00	
6GT2803-1BA10	
6GT2810-2AB00	
6GT2810-2AB01	
6GT2810-2AB02-0AX	0 3/8
6GT2810-2AB03	
6GT2810-2AC00	
6GI2810-2AC10	
6G12810-2AC80	
6G12810-2AE81-0AX	1
6GT2810-2AG00	
6GT2810-2AG10	
6GT2810-2AG80	
6G12810-2BB80	
6G12810-2BB80-0AX	0 3/15
6GT2810-2DC00	
6GT2810-2DC10	
6GT2810-2EC00	
6GT2810-2EC10	
CCT2010-2EEUU	
CT2010-2EEU1	
6GT2910 2HC90	/ 1 / כ
6GT2810-4HCR0	2/10
6GT2811_64A10 0AA	0 مرابع مرابع
6GT2811-64410-144	عد/عد ۵۵/۵
6GT2811-6AA10-2AA	0 2/36
6GT2811-6AB20-044	0
6GT2811-6AB20-1AA	0
6GT2811-6AB20-2AA	0
6GT2811-6CA10-0AA	0
6GT2811_6CA10_1AA	0

6G12811-6CA10-	2AA0	.3/40
6GT2812-0AA00.		.3/52
6GT2812-0AA01		.3/52
6GT2812-0GA08		.3/49
6GT2812-1EA00.		.3/46
6GT2812-1EA01		.3/46
6GT2812-1GA08		.3/49
6GT2813-0CA00		.3/43
6GT2813-0CA10		.3/43
6G12815-0BH10		3/52
6G12815-0BH30		3/52
6G12815-0BN10		3/52
6G12815-0BN20		3/52
6G12815-0BN40		3/52
6G12815-1BN10		3/52
CCT2015-20010		3/52
CT2013-2DN13		3/32
6GT2921 1AC10		2/101
6GT2921 1AC22		2/01 2/91
6GT2921-1AC32		2/01
6GT2821-2AC10		2/85
6GT2821-4AC10		2/88
6GT2821-4AC10		2/88
6GT2821-4AC32		2/88
6GT2821-5AC10		2/93
6GT2821-5AC32		2/93
6GT2821-5AC40		2/93
6GT2821-6AC10		.2/97
6GT2821-6AC32		.2/97
6GT2821-6AC40		2/97
6GT2823-0AA00.		.2/82
6GT2890-0AA00		3/52
6GT2890-0AB00		3/40
6GT2891-0CH50		3/40
6GT2891-0PH50.		3/40
6GT2891-4EH20		5/26
6GT2891-4EH50.		5/26
6GT2891-4FH20.		5/15,
	5/18, 5/20, 5/24,	5/26
6G12891-4FH50.		5/15, 5/26
6GT2891-4EN10	4/10, 4/00, E/0	0,20
	4/18 4/29 5/8	5/15
		5/15, 5/26
6GT2891-4FN20.	4/18, 4/29, 5/8, 5/18, 5/20, 5/24, 4/18, 4/29, 5/8,	5/15, 5/26 5/15,
6GT2891-4FN20.		5/15, 5/26 5/15, 5/26
6GT2891-4FN20 6GT2891-4FN50		5/15, 5/26 5/15, 5/26 5/15, 5/26
6GT2891-4FN20 6GT2891-4FN50		5/15, 5/26 5/15, 5/26 5/15, 5/26 5/26
6GT2891-4FN20 6GT2891-4FN50 6GT2891-4JH20 6GT2891-4JH50		5/15, 5/26 5/15, 5/26 5/15, 5/26 5/26 5/26
6GT2891-4FN20 6GT2891-4FN50 6GT2891-4JH20 6GT2891-4JH50 6GT2891-4JH50		5/15, 5/26 5/15, 5/26 5/15, 5/26 5/26 5/26 5/26 5/26
6GT2891-4FN20 6GT2891-4FN50 6GT2891-4JH20 6GT2891-4JH50 6GT2891-4JH50 6GT2891-4JN10 6GT2891-4KH50		5/15, 5/26 5/15, 5/26 5/26 5/26 5/26 5/26 5/26 5/26 /101.
6GT2891-4FN20. 6GT2891-4FN50. 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4KH50		5/15, 5/26 5/15, 5/26 5/26 5/26 5/26 5/26 5/26 5/26 /101, 5/26
6GT2891-4FN20. 6GT2891-4FN50. 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4KH50. 6GT2891-4KH50-		5/15, 5/26 5/15, 5/26 5/26 5/26 5/26 5/26 5/26 /101, 5/26 /101,
6GT2891-4FN20 6GT2891-4FN50 6GT2891-4JH20 6GT2891-4JH50 6GT2891-4JH50 6GT2891-4KH50 6GT2891-4KH50		5/15, 5/26 5/15, 5/26 5/26 5/26 5/26 5/26 5/26 5/26 5/26
6GT2891-4FN20 6GT2891-4FN50 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JN10. 6GT2891-4KH50. 6GT2891-4KH50 6GT2891-4LH50		5/15, 5/26 5/15, 5/26 5/26 5/26 5/26 5/26 5/26 5/26 (101, 5/26 /101, 5/26 /101, 5/26
6GT2891-4FN20. 6GT2891-4FN50. 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JN10. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50.		5/15, 5/26 5/15, 5/26 5/26 5/26 5/26 5/26 5/26 5/26 5/26
6GT2891-4FN20. 6GT2891-4FN50. 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4LH50. 6GT2891-4LN10. 6GT2891-4LN10. 6GT2891-4LN10.		5/15, 5/26 5/15, 5/26 5/26 5/26 5/26 5/26 5/26 (101, 5/26 (101, 5/26 (101, 5/26 2/97 2/97 2/97
6GT2891-4FN20. 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4JN10. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4LH50.		5/15, 5/26 5/15, 5/26 5/26 5/26 5/26 5/26 5/26 5/26 (101, 5/26 (101, 5/26 2/97 2/97 2/97 2/97
6GT2891-4FN20 6GT2891-4JH20. 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JN10. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4LN10. 6GT2891-4LN10. 6GT2891-4MN10. 6GT2891-0EA00. 6GT2894-0EA00.		5/15, 5/26 5/15, 5/26 5/26 5/26 5/26 5/26 5/26 5/26 5/26 5/26 2/97 2/97 2/97 2/97 2/97 2/97
6GT2891-4FN20. 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4JN10. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4MH50. 6GT2891-4MH50. 6GT2891-4MH50. 6GT2898-0AA00. 6GT2898-0AA00. 6GT2898-0AA01.		5/15, 5/26 5/15, 5/26 5/15, 5/26 5/26 5/26 5/26 5/26 5/26 5/26 101, 5/26 101, 5/26 2/97 2/97 2/97 2/97 2/97 2/97 3/40
6GT2891-4FN20. 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4JN10. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4MN10. 6GT2894-0EA00. 6GT2898-0A00. 6GT2898-0A00.		5/15,5/26 5/15,5/26 5/15,5/26 5/26 5/26 5/26 5/26 5/26 5/26 5/26
6GT2891-4FN20. 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4JN10. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4MN10. 6GT2891-4MN10. 6GT2898-0AA00. 6GT2898-0AA00. 6GT2898-0AA20. 6GT2898-0AA20. 6GT2898-0APB00. 6GT289		5/15,5/26 5/15,5/26 5/26 5/26 5/26 5/26 5/26 5/26 (101, 5/26 2/97 2/97 2/97 2/97 2/97 2/97 2/97 2/97
6GT2891-4FN20. 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2892-0AA00. 6GT2898-0AA00. 6GT2898-0AA00. 6GT2898-0AB00. 6GT2898-0CB00.		5/15,5/26 5/15,5/26 5/26 5/26 5/26 5/26 5/26 5/26 5/26
6GT2891-4FN20. 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2898-0AA00. 6GT2898-0AA00. 6GT2898-0AA00. 6GT2898-0BB00. 6GT2898-0CB00 6GT2898-0CB00		5/15,5/26 5/26,5/15,5/26 5/26,5/26 5/26,5/26 5/26 5/26 5/26 5/26 7/26 7/26 7/26 7/29 2/97 2/97 2/97 2/97 2/97 2/97 3/40 3/40 3/40 3/43 3/43
6GT2891-4FN20. 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4MH50. 6GT2898-0AA00. 6GT2898-0AA00. 6GT2898-0AA00. 6GT2898-0CB00.		5/15,5/26 5/26,5/15,5/26 5/26,5/26 5/26,5/26 5/26 5/26 5/26 5/26 5/26 5/26 5/26
6GT2891-4FN20. 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4JN10. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4KH50. 6GT2891-4MH50. 6GT2898-0AA00. 6GT2898-0AA00. 6GT2898-0AA00. 6GT2898-0CB00. 6GT2898-0CB00. 6GT2898-0CB00. 6GT2898-0CB00. 6GT2898-0CB00. 6GT2898-2AA00. 6GT2898-2AA00. 6GT2898-2AA00. 6GT2898-2AA00. 6GT2898-3AA00.		5/15, 5/26 5/26 5/26 5/26 5/26 5/26 5/26 5/26 5/26
6GT2891-4FN20. 6GT2891-4JH20. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4JH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2891-4LH50. 6GT2898-0AA00. 6GT2898-0AA00. 6GT2898-0BB00. 6GT2898-0CB00 6GT2898-0CB00. 6GT2898-0CB00. 6GT2898-2AA00. 6GT2898-3AA00.		5/15, 5/26 5/26, 5/26 5/26, 5/26 5/26, 5/26 5/26, 5/26 5/26, 101, 5/26 2/97 2/97 2/97 2/97 2/97 2/97 3/40 3/40 3/40 3/40 3/40 3/40 3/40 3/40

6XV1
6XV1822-5BE305/7, 5/13
6XV1822-5BE50
6XV1822-5BH10 5/7, 5/13
6XV1822-5BH155/7, 5/13
6XV1822-5BH20 5/7, 5/13
6XV1822-5BH30 5/7, 5/13
6XV1822-5BH50 5/7, 5/13
6XV1822-5BN10 5/7, 5/13
6XV1822-5BN15 5/7, 5/13
6XV1830-0EH105/8
6XV1830-3DE30
6XV1830-3DE50
6XV1830-3DH10
6XV1830-3DH15
6XV1830-3DH20
6XV1830-3DH30
6XV1830-3DH50 5/7
6XV1830-3DN10 5/7
6XV/1830-3DN15 5/7
6XV1830-74H10 5/7
6XV/1830-7BH05 5/7
6XV/1830-7BH10
6XV/1830-7BH15
6XV1830-7BH30 5/7
0/ 1030-7 BH30
0XV1830-7 BH30
6XV1830-7BN10
6XV1830-7BN15
6XV1830-7BN20
6XV1830-7BN25
6XV1830-7BN30
6XV1830-7BN35
6XV1830-7BN405/7
6XV1830-7BN455/7
6XV1830-7BN505/7
6XV1830-8AH105/8, 5/15
6XV1840-2AH10
6XV1870-3QN10
6XV1870-8AE30 4/17, 4/28, 5/13
6XV1870-8AE50 4/17, 4/28, 5/13
6XV1870-8AH10 4/17, 4/28, 5/13
6XV1870-8AH15 4/17, 4/28, 5/13
6XV1870-8AH20 4/17, 4/28, 5/13
6XV1870-8AH30 4/17, 4/28, 5/13
6XV1870-8AH50 3/36, 3/40, 4/17, 4/28, 5/13
6XV1870-8AN10 4/17, 4/28, 5/13
6XV1870-8AN15 4/17, 4/28, 5/13
6XV1871-5Bxxx
6XV1871-5TH20 4/17, 4/28, 5/14
6XV1871-5TH30 4/17, 4/28, 5/14
6XV1871-5TH503/36, 3/40, 4/17, 4/28, 5/14
6XV1871-5TN10
6XV1871-5TN15

© Siemens AG 2016

Appendix

Notes

Appendix

Conditions of sale and delivery

1. General Provisions

By using this catalog you can acquire hardware and software products described therein from Siemens AG subject to the following Terms and Conditions of Sale and Delivery (hereinafter referred to as "T&C"). Please note that the scope, the quality and the conditions for supplies and services, including software products, by any Siemens entity having a registered office outside Germany, shall be subject exclusively to the General Terms and Conditions of the respective Siemens entity. The following T&C apply exclusively for orders placed with Siemens Aktiengesellschaft, Germany.

1.1 For customers with a seat or registered office in Germany

For customers with a seat or registered office in Germany, the following applies subordinate to the T&C:

- the "General Terms of Payment"1) and,
- for software products, the "General License Conditions for Software Products for Automation and Drives for Customers with a Seat or Registered Office in Germany"¹⁾ and,
- for other supplies and services, the "General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry"¹⁾.

1.2 For customers with a seat or registered office outside Germany

For customers with a seat or registered office outside Germany, the following applies subordinate to the T&C:

- the "General Terms of Payment"¹⁾ and,
- for software products, the "General License Conditions for Software Products for Automation and Drives for Customers with a Seat or Registered Office outside of Germany"¹⁾ and

for other supplies and/or services, the "General Conditions for Supplies of Siemens Industry for Customers with a Seat or Registered Office outside of Germany"¹).

2. Prices

The prices are in € (Euro) ex point of delivery, exclusive of packaging.

The sales tax (value added tax) is not included in the prices. It shall be charged separately at the respective rate according to the applicable statutory legal regulations.

Prices are subject to change without prior notice. We will charge the prices valid at the time of delivery.

To compensate for variations in the price of raw materials (e.g. silver, copper, aluminum, lead, gold, dysprosium and neodym), surcharges are calculated on a daily basis using the so-called metal factor for products containing these raw materials. A surcharge for the respective raw material is calculated as a supplement to the price of a product if the basic official price of the raw material in question is exceeded.

The metal factor of a product indicates the basic official price (for those raw materials concerned) as of which the surcharges on the price of the product are applied, and with what method of calculation.

You will find a detailed explanation of the metal factor on the page headed "Metal surcharges".

To calculate the surcharge (except in the cases of dysprosium and neodym), the official price from the day prior to that on which the order was received or the release order was effected is used.

To calculate the surcharge applicable to dysprosium and neodym ("rare earths"), the corresponding three-month basic average price in the quarter prior to that in which the order was received or the release order was effected is used with a one-month buffer (details on the calculation can be found in the explanation of the metal factor).

3. Additional Terms and Conditions

The dimensions are in mm. In Germany, according to the German law on units in measuring technology, data in inches apply only to devices for export.

Illustrations are not binding.

Insofar as there are no remarks on the individual pages of this catalog - especially with regard to data, dimensions and weights given - these are subject to change without prior notice.

4. Export regulations

We shall not be obligated to fulfill any agreement if such fulfillment is prevented by any impediments arising out of national or international foreign trade or customs requirements or any embargoes and/or other sanctions.

Export of goods listed in this catalog may be subject to licensing requirements. We will indicate in the delivery details whether licenses are required under German, European and US export lists. Goods labeled with "AL" not equal to "N" are subject to European or German export authorization when being exported out of the EU. Goods labeled with "ECCN" not equal to "N" are subject to US re-export authorization.

The export indications can be viewed in advance in the description of the respective goods on the Industry Mall, our online catalog system. Only the export labels "AL" and "ECCN" indicated on order confirmations, delivery notes and invoices are authoritative.

Even without a label, or with label "AL:N" or "ECCN:N", authorization may be required i.a. due to the final disposition and intended use of goods.

If you transfer goods (hardware and/or software and/or technology as well as corresponding documentation, regardless of the mode of provision) delivered by us or works and services (including all kinds of technical support) performed by us to a third party worldwide, you must comply with all applicable national and international (re-)export control regulations.

If required for the purpose of conducting export control checks, you (upon request by us) shall promptly provide us with all information pertaining to the particular end customer, final disposition and intended use of goods delivered by us respectively works and services provided by us, as well as to any export control restrictions existing in this relation.

The products listed in this catalog may be subject to European/German and/or US export regulations. Any export requiring approval is therefore subject to authorization by the relevant authorities.

Errors excepted and subject to change without prior notice.

 The text of the Terms and Conditions of Siemens AG can be downloaded at www.siemens.com/automation/salesmaterial-as/catalog/en/terms_of_trade_en.pdf
Catalogs

Digital Factory, Process Industries and Drives and Energy Management

Further information can be obtained from our branch offices listed at www.siemens.com/automation/partner

Interactive Catalog on DVD Products for Automation and Drives	Catalog CA 01
Building Control	
GAMMA Building Control	ET G1
Drive Systems	
SINAMICS G130 Drive Converter Chassis Units SINAMICS G150 Drive Converter Cabinet Units	D 11
SINAMICS GM150, SINAMICS SM150 Medium-Voltage Converters	D 12
SINAMICS PERFECT HARMONY GH180 Medium-Voltage Air-Cooled Drives Germany Edition	D 15.1
SINAMICS G180 Converters – Compact Units, Cabinet Systems, Cabinet Units Air-Cooled and Liquid-Cooled	D 18.1
SINAMICS S120 Chassis Format Units and Cabinet Modules	D 21.3
SINAMICS DCM DC Converter, Control Module SINAMICS DCM Cabinet	D 23.1 D 23.2
SINAMICS Inverters for Single-Axis Drives and SIMOTICS Motors	D 31
SINAMICS G120P and SINAMICS G120P Cabinet pump, fan, compressor converters	D 35
LOHER VARIO High Voltage Motors Flameproof, Type Series 1PS4, 1PS5, 1MV4 and 1MV5 Frame Size 355 to 1000, Power Range 80 to 7100 kW	D 83.2
Three-Phase Induction Motors SIMOTICS HV, SIMOTICS TN • Series H-compact • Series H-compact PLUS	D 84.1
High Voltage Three-phase Induction Motors	D 84.9
Three-Phase Induction Motors SIMOTICS HV,	D 86.1
Synchronous Motors with Permanent-Magnet Technology, HT-direct	D 86.2
DC Motors SIMOREG DC MASTER 6RA70 Digital Chassis Converters	DA 12 DA 21.1
SIMOREG K 6RA22 Analog Chassis Converters Digital: SIMOREG DC MASTER 6RM70 Digital Converter Cabinet Units	DA 21.2 <i>DA 22</i>
SIMOVERT PM Modular Converter Systems	DA 45
SIEMOSYN Motors MICROMASTER 420/430/440 Inverters	DA 48 DA 51 2
MICROMASTER 411/COMBIMASTER 411	DA 51.3
SIMOTICS Low-Voltage Motors	D 81.1
SIMOTICS FD Low-Voltage Motors	D 81.8
LOHER Low-Voltage Motors	D 83.1
MUTUX Geared Motors	D 87.1
SIMOGEAR Gearboxes with adapter	MD 50.11 MD 50.11
Mechanical Driving Machines FLENDER Standard Couplings	MD 10.1
FLENDER High Performance Couplings	MD 10.2
FLENDER Backlash-free Couplings FLENDER SIP Standard industrial planetary gear units	MD 10.3 MD 31.1
Process Instrumentation and Analytics	
Digital: Field Instruments for Process Automation	FI 01
Digital: SIPART Controllers and Software	MP 31
Products for Weighing Technology	VVI 10 AP 01
Digital: Process Analytics, Components for Continuous	AP 11

Emission Monitoring

Low-Voltage Power Distribution and	Catalog
SENTRON · SIVACON · ALPHA	LV 10
Protection, Switching, Measuring and Monitoring Devices, Switchboards and Distribution Systems	
Standards-Compliant Components for Photovoltaic Plants	LV 11
Electrical Components for the Railway Industry	LV 12
TÜV-certified Power Monitoring System	LV 14
Components for Industrial Control Panels according to UL Standards	LV 16
3WT Air Circuit Breakers up to 4000 A	LV 35
3VT Molded Case Circuit Breakers up to 1600 A	LV 36
Digital: SIVACON System Cubicles, System Lighting and System Air-Conditioning	LV 50
Digital: ALPHA Distribution Systems	LV 51
ALPHA FIX Terminal Blocks	LV 52
SIVACON S4 Power Distribution Boards	LV 56
SIVACON 8PS Busbar Trunking Systems	LV 70
Digital: DELTA Switches and Socket Outlets	ET D1
Motion Control	
SINUMERIK 840	NC 62
Equipment for Machine Tools	
SINUMERIK 808	NC 81.1
Equipment for Machine Tools	
SINUMERIK 828	NC 82
Equipment for Machine Tools	D MAA
SIMOTION, SINAMICS S120 & SIMOTICS	PM 21
Digital: Drive and Control Components for Cranes	CR 1
Power Supply	
SITOP Power supply	KT 10.1
Safety Integrated	
Safety Technology for Factory Automation	SI 10
,,,	
SIMATIC HMI / PC-based Automation	
SIMATIC HMI / PC-based Automation Human Machine Interface Systems/	ST 80/
SIMATIC HMI / PC-based Automation Human Machine Interface Systems/ PC-based Automation	ST 80/ ST PC
SIMATIC HMI / PC-based Automation Human Machine Interface Systems/ PC-based Automation	ST 80/ ST PC
SIMATIC HMI / PC-based Automation Human Machine Interface Systems/ PC-based Automation SIMATIC Ident Industrial Identification Systems	ST 80/ ST PC
 SIMATIC HMI / PC-based Automation Human Machine Interface Systems/ PC-based Automation SIMATIC Ident Industrial Identification Systems SIMATIC Industrial Automation Systems 	ST 80/ ST PC ID 10
 SIMATIC HMI / PC-based Automation Human Machine Interface Systems/ PC-based Automation SIMATIC Ident Industrial Identification Systems SIMATIC Industrial Automation Systems Products for Totally Integrated Automation 	ST 80/ ST PC ID 10 ST 70
 SIMATIC HMI / PC-based Automation Human Machine Interface Systems/ PC-based Automation SIMATIC Ident Industrial Identification Systems SIMATIC Industrial Automation Systems Products for Totally Integrated Automation SIMATIC PCS 7 Process Control System 	ST 80/ ST PC ID 10 ST 70 ST PCS 7
 SIMATIC HMI / PC-based Automation Human Machine Interface Systems/ PC-based Automation SIMATIC Ident Industrial Identification Systems SIMATIC Industrial Automation Systems Products for Totally Integrated Automation SIMATIC PCS 7 Process Control System System components 	ST 80/ ST PC ID 10 ST 70 ST PCS 7
 SIMATIC HMI / PC-based Automation Human Machine Interface Systems/ PC-based Automation SIMATIC Ident Industrial Identification Systems SIMATIC Industrial Automation Systems Products for Totally Integrated Automation SIMATIC PCS 7 Process Control System System components 	ST 80/ ST PC ID 10 ST 70 ST PCS 7 ST PCS 7 T
 SIMATIC HMI / PC-based Automation Human Machine Interface Systems/ PC-based Automation SIMATIC Ident Industrial Identification Systems SIMATIC Industrial Automation Systems Products for Totally Integrated Automation SIMATIC PCS 7 Process Control System System components SIMATIC PCS 7 Process Control System Technology components Add-ons for the SIMATIC PCS 7 Process Control System 	ST 80/ ST PC ID 10 ST 70 ST PCS 7 ST PCS 7 T ST PCS 7 AO
 SIMATIC HMI / PC-based Automation Human Machine Interface Systems/ PC-based Automation SIMATIC Ident Industrial Identification Systems SIMATIC Industrial Automation Systems Products for Totally Integrated Automation SIMATIC PCS 7 Process Control System System components SIMATIC PCS 7 Process Control System Technology components Add-ons for the SIMATIC PCS 7 Process Control System 	ST 80/ ST PC ID 10 ST 70 ST PCS 7 ST PCS 7 T ST PCS 7 AO
 SIMATIC HMI / PC-based Automation Human Machine Interface Systems/ PC-based Automation SIMATIC Ident Industrial Identification Systems SIMATIC Industrial Automation Systems Products for Totally Integrated Automation SIMATIC PCS 7 Process Control System System components SIMATIC PCS 7 Process Control System Technology components Add-ons for the SIMATIC PCS 7 Process Control System SIMATIC NET Industrial Communication 	ST 80/ ST PC ID 10 ST 70 ST PCS 7 ST PCS 7 T ST PCS 7 AO IK PI
 SIMATIC HMI / PC-based Automation Human Machine Interface Systems/ PC-based Automation SIMATIC Ident Industrial Identification Systems SIMATIC Industrial Automation Systems Products for Totally Integrated Automation SIMATIC PCS 7 Process Control System System components SIMATIC PCS 7 Process Control System Technology components Add-ons for the SIMATIC PCS 7 Process Control System SIMATIC NET Industrial Communication 	ST 80/ ST PC ID 10 ST 70 ST PCS 7 ST PCS 7 T ST PCS 7 AO IK PI
 SIMATIC HMI / PC-based Automation Human Machine Interface Systems/ PC-based Automation SIMATIC Ident Industrial Identification Systems SIMATIC Industrial Automation Systems Products for Totally Integrated Automation SIMATIC PCS 7 Process Control System System components SIMATIC PCS 7 Process Control System Technology components Add-ons for the SIMATIC PCS 7 Process Control System SIMATIC NET Industrial Communication SIRIUS Industrial Controls Digital: SIRIUS Industrial Controls 	ST 80/ ST PC ID 10 ST 70 ST PCS 7 ST PCS 7 T ST PCS 7 AO IK PI <i>IC 10</i>
 SIMATIC HMI / PC-based Automation Human Machine Interface Systems/ PC-based Automation SIMATIC Ident Industrial Identification Systems SIMATIC Industrial Automation Systems Products for Totally Integrated Automation SIMATIC PCS 7 Process Control System System components SIMATIC PCS 7 Process Control System Technology components Add-ons for the SIMATIC PCS 7 Process Control System SIMATIC NET Industrial Communication SIRIUS Industrial Controls Digital: SIRIUS Industrial Controls Digital: These catalogs are only available as a PDF. 	ST 80/ ST PC ID 10 ST 70 ST PCS 7 ST PCS 7 T ST PCS 7 AO IK PI <i>IC 10</i>

Digital versions of the catalogs are available on the Internet at:

www.siemens.com/industry/infocenter There you'll find additional catalogs in other languages.

Please note the section "Downloading catalogs" on page "Online services" in the appendix of this catalog.

Security information:

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates.

For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit http://www.siemens.com/industrialsecurity.

To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit http://support.industry.siemens.com

Siemens Industry, Inc. 5300 Triangle Parkway Norcross, GA 30092 U.S.A. Subject to change without prior notice Article No. E86060-K8310-A101-B1-7600 W-FPN6Z-PD-PAK06 / Dispo 26107 KG 0216 1.0 DPG 322 En Printed in Germany © Siemens AG 2016 The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract. Availability and technical specifications are subject to change without notice. All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.