



Siemens
Industry
Online
Support

Manual

SIMATIC PCS 7

Standard Architectures

SIMATIC PCS 7 V10

SIEMENS

Legal information

Warning notice system

This manual contains notices you have to observe in order to ensure your personal safety, as well as to prevent damage to property. The notices referring to your personal safety are highlighted in the manual by a safety alert symbol, notices referring only to property damage have no safety alert symbol. These notices shown below are graded according to the degree of danger.



DANGER

Indicates that death or severe personal injury will result if proper precautions are not taken.



WARNING

Indicates that death or severe personal injury may result if proper precautions are not taken.



CAUTION

Indicates that minor personal injury can result if proper precautions are not taken.

NOTICE

Indicates that property damage can result if proper precautions are not taken.

If more than one degree of danger is present, the warning notice representing the highest degree of danger will be used. A notice warning of injury to persons with a safety alert symbol may also include a warning relating to property damage.

Qualified Personnel

The product/system described in this documentation may be operated only by personnel qualified for the specific task in accordance with the relevant documentation, in particular its warning notices and safety instructions. Qualified personnel are those who, based on their training and experience, are capable of identifying risks and avoiding potential hazards when working with these products/systems.

Proper use of Siemens products

Note the following:



WARNING

Siemens products may only be used for the applications described in the catalog and in the relevant technical documentation. If products and components from other manufacturers are used, these must be recommended or approved by Siemens. Proper transport, storage, installation, assembly, commissioning, operation and maintenance are required to ensure that the products operate safely and without any problems. The permissible ambient conditions must be complied with. The information in the relevant documentation must be observed.

Trademarks

All names identified by ® are registered trademarks of Siemens AG. The remaining trademarks in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owner.

Disclaimer of Liability

We have reviewed the contents of this publication to ensure consistency with the hardware and software described. Since variance cannot be precluded entirely, we cannot guarantee full consistency. However, the information in this publication is reviewed regularly and any necessary corrections are included in subsequent editions.

Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, systems, machines and networks.

In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial security concept. Siemens' products and solutions only form one element of such a concept.

Customer is responsible to prevent unauthorized access to its plants, systems, machines and networks. Systems, machines and components should only be connected to the enterprise network or the internet if and to the extent necessary and with appropriate security measures (e.g. use of firewalls and network segmentation) in place.

Additionally, Siemens' guidance on appropriate security measures should be taken into account. For more information about industrial security, please visit <https://www.siemens.com/industrialsecurity>.

Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends to apply product updates as soon as available and to always use the latest product versions. Use of product versions that are no longer supported, and failure to apply latest updates may increase customer's exposure to cyber threats.

To stay informed about product updates, subscribe to the Siemens Industrial Security RSS Feed under <https://www.siemens.com/industrialsecurity>.

Table of contents

1.	Introduction	7
2.	Selection Guide	9
2.1.	Single Station	10
2.2.	Multi-User System	10
2.3.	Client-Server System.....	11
2.4.	Client-Server System with Several Servers.....	11
3.	Single Station.....	12
3.1.	Single Station with Dual Monitor	12
3.2.	Single Station with PCS 7 Web Server	14
4.	System with Multiple OS Single Stations	16
4.1.	Multiple OS Single Stations with Dual Monitor	17
4.2.	Redundant OS Single Station.....	19
4.3.	Plain System Configuration without OS Server	21
5.	OS Client/OS Server System	23
5.1.	OS Client/OS Server with Operator Control and Monitoring on the ES and OS Server	24
5.2.	OS Client/OS Server Operation on a Redundant Server Architecture	26
5.3.	OS Client/OS Server System with a PCS 7 Web Server.....	28
5.4.	OS Client/OS Server System with Terminal Server	30
5.5.	OS Client/OS Server System with DataMonitor Server	32
5.6.	OS Client/OS Server with Dual Monitor	34
5.7.	OS Client/OS Server System with Multi-User Engineering	36
6.	SIMATIC BATCH	38
6.1.	SIMATIC BATCH Single Station.....	39
6.2.	SIMATIC BATCH Single Station in an OS Client/OS Server Architecture	41
6.3.	SIMATIC BATCH OS Client/OS Server	43
6.4.	Separate SIMATIC BATCH Server	45
6.5.	Redundant SIMATIC BATCH Client-Server Architecture.....	47
6.6.	SIMATIC BATCH Client-Server Architecture Redundant (OS + SB Server Separated).....	49
7.	SIMATIC Route Control.....	51
7.1.	SIMATIC Route Control Single Station	52
7.2.	SIMATIC Route Control Client-Server Architecture	54
7.3.	Redundant SIMATIC Route Control Client/ServerArchitecture	56
7.4.	SIMATIC Route Control Client/Server Architecture Redundant (OS + RCS Server Separated).....	58

8.	SIMATIC Route Control and SIMATIC BATCH	60
9.	Archiving	62
9.1.	OS Client/OS Server	63
9.2.	Redundant OS Server Pair and Process Historian.....	65
10.	Fieldbus	68
10.1.	DP-PA/DP-FF Fieldbus	70
10.2.	Single Optical DP-PA/DP-FF Fieldbus	73
10.3.	Redundant DP-PA/DP-FF Fieldbus.....	76
10.4.	Redundant Optical DP-PA/DP-FF Fieldbus	79
10.5.	PROFINET Fieldbus with a Standard Automation System	82
10.6.	PROFINET Fieldbus with a High-Availability Automation System - Simple System Redundancy S2.....	84
10.7.	Redundant PROFINET Fieldbus with a High-Availability Automation System - R1	87
11.	SIMATIC PDM.....	89
11.1.	Local Service and Parameterization Station on the Fieldbus	90
11.2.	Local Service and Parameterization Station on the System Bus.....	92
11.3.	SIMATIC PDM and PCS 7 Single Station	93
11.4.	SIMATIC PDM and PCS 7 OS Client/OS Server System	95
11.5.	SIMATIC PDM and Non-SIMATIC S7 Master.....	97
11.6.	SIMATIC PDM Stand-Alone Server	99
12.	Maintenance Station (Asset Management)	101
12.1.	PCS 7 Maintenance Station in Single Station	103
12.2.	PCS 7 Maintenance Station in a Multi-User System with MS/OS Clients and Combined MS/OS Server	107
12.3.	PCS 7 Maintenance Station in a Multi-User System with MS/OS Clients and Separate MS Server and Red. OS Server	112
12.4.	PCS 7 Maintenance Station in a Multi-User System with MS/OS Clients and Separate Redundant MS Server Pair and OS Server Pair	114
12.5.	Asset Management in Flat Hierarchies	119
12.6.	SIMATIC PDM Maintenance Station.....	121
13.	SIMATIC Management Console	122
13.1.	Basic Functions of the Management Console	122
13.2.	Functions of the Management Console.....	122
13.2.1.	Functions for Software Administration	122
13.2.2.	Functions for Determining Inventory Data	123
14.	Network Architecture	125
14.1.	Overview	125
14.2.	Ring Architectures	127
14.2.1.	High-Speed Ring Error Tolerance	127

14.2.2.	Ring Connectivity, Standby Redundancy	128
14.2.3.	MRP	129
14.2.4.	MRP Interconnection	129
14.3.	Redundancy Concepts – Terminal Bus	130
14.3.1.	Introduction	130
14.3.2.	Redundant Terminal Bus	131
14.4.	Redundancy Concepts – System Bus	132
14.4.1.	Introduction	132
14.4.2.	Standard Automation System	132
14.4.3.	High-Availability Automation System AS 410	134
14.5.	Sample Configurations	136
14.5.1.	Fault-tolerant Ring Architectures with Glass Fiber	136
14.5.2.	Electrical fault-tolerant Ring Architectures	138
14.5.3.	Electrical fault-tolerant Ring Structures with Combined System and Terminal Bus	139
14.5.4.	Redundant Bus Architectures with fault-tolerant Rings	140
14.5.5.	Redundant Bus Architectures with fault-tolerant Rings and Combined System and Terminal Bus	141
15.	Process Safety	142
16.	24V DC Supply Concepts	143
16.1.	Basic Power Supplies	145
16.2.	Redundant Power Supply	146
16.3.	Redundant Power Supply System	147
16.4.	Redundant Power Supply with Selective Monitoring of the 24V Feeders	148
16.5.	Device Combination of Power Supply and SITOP Selectivity System SEL1600 IOL	150
16.6.	Buffered Power Supply	152
16.7.	Redundant Power Supply with Buffering	154
16.8.	Redundant Power Supply with Redundant Buffering	156
16.9.	Power Supply System with Selective Monitoring and Buffering	158
17.	Possibilities for Data Exchange	160
17.1.	Small OS Client/OS Server System and OpenPCS 7	161
17.2.	Large OS Client/OS Server System and OpenPCS 7	163
18.	AS-OS PO Counting	166
18.1.	Process Objects	166
18.2.	Cumulative Licenses	167
19.	Service and support	168
20.	Appendix	169
20.1.	Links and literature	169
20.2.	Document history	169

1. Introduction

This document describes the architectures and components of SIMATIC PCS 7 in a basic structure. In addition to the mentioned architectures, various options and configured versions are also displayed. SIMATIC PCS 7 is a highly scalable process control system with numerous topologies that are based on redundancy as well as optional hardware and software features.

This document should help you by simplifying your choice:

- Architectures based on the number of users, inputs and outputs
- SIMATIC PCS 7-Optionen, for example. SIMATIC BATCH, SIMATIC Route Control, Asset management and Fieldbus
- Degree of system availability and network topologies
- Power supply concepts for DC 24V

The various configurations in this document are compared on the basis of schematic diagrams and a sample component list.

NOTE

The architectures shown in this document contain only the necessary basic licenses. In order to achieve the desired quantity structure, in addition to the basic licenses, you must also take into account the corresponding set of volume licenses.

NOTE


The components on the parts lists refer to the 2021 PCS 7 catalog: <https://www.siemens.de/STPCS7>
You may need to check whether more up-to-date components are available.

NOTE

The parts lists for the individual configurations do not contain any network components, since a large number of variants are available for this.
To do this, use Section [14](#), Network Architecture.

Furthermore you will find the manual "PCS 7 – PC Configuration V10.0" under the following link:
<https://support.industry.siemens.com/cs/ww/en/view/109973495>.

This document contains additional information about the PC components that are used with PCS 7.



NOTE

This legend shows schematic representations of the components and does not show the real picture of the individual components, as their shape, the terminal type and the modular structure of the selected components may be different.

2. Selection Guide

At the planning stage, the task is to create a Distributed Control System (DCS) with a scalable and flexible architecture.

The sample configurations that are listed below will help you to choose the right configuration to meet your requirements and demands of the properties you need like the size, availability and number of operator stations.

Every configuration in this document contains a parts list that provides an overview of the PCS 7 components that are used.

When choosing your architecture, you should first determine the following system criteria:

1. Number of inputs and outputs for the process
2. Number of operators that work with the system

Number of inputs and outputs connected to the system

To determine the number of signals entering or leaving the system, you must consider several resources:

3. The number of digital and analog I/Os to be installed.
4. The number of variables (boolean, integer or floating point) exchanged between the PCS 7 system and external systems such as PLCs, serial interfaces, etc., and running on protocols such as Modbus, PROFIBUS, PROFINET or Ethernet.
5. Inputs and outputs that are read or written via bus systems, such as AS-Interface.


Number of persons operating the system

The chosen architecture must be designed for the total number of users, operators and engineers who will work on the system in the future. This number determines the required number of individual workplaces.


NOTE

SIMATIC PCS 7 enables a seamless extension of your system with full use of existing equipment. Both software components and hardware components satisfy this requirement equally.


2.1. Single Station




2.2. Multi-User System



2.3. Client-Server System



2.4. Client-Server System with Several Servers



3. Single Station

Single station

For small systems where engineering or operation tasks are carried out by only one user the single-user architecture of PCS 7 offers a cost-effective solution. In this architecture, the functionality of the Engineering Station (ES) and the Operator Station (OS) is integrated into one PC.


Dual monitor

A Single Station or an Engineering Station can be expanded with a standard graphics card that makes it possible to connect up to two monitors.

The system can be expanded with an additional multi graphics card (2 additional monitor connections) so that up to four monitors can be connected to one system.

3.1. Single Station with Dual Monitor

This configuration is a system in which the ES and OS are used on one PC as a single station with two monitors.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station and Operator Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	3)
1		6ES7651-5AA78-0YA0	SIMATIC PCS 7, SOFTWARE, ES SINGLE STATION V10.0 (AS/OS: PO 250)	1)
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
Automation system				
1		6ES7654-6CL03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, SYSTEM EXPANSIONS CARD 500 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, UC 120/230V 10A POWER SUPPLY	1) 2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE


¹⁾ The number of POs can be increased later by means of extra volume licenses.

²⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

³⁾ Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

3.2. Single Station with PCS 7 Web Server

This configuration is a station in which the ES, OS, and PCS 7 Web Server are used on one PC as a single station. The PCS 7 Web Clients are connected via the terminal bus.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station and Operator Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
1		6ES7651-5AA78-0YA0	SIMATIC PCS 7, SOFTWARE, ES SINGLE STATION V10.0 (AS/OS: PO 250)	1)
1		6ES7658-2HX78-2YB0	SOFTWARE SIMATIC PCS 7 WEB DIAGNOSE SERVER V10.0	4)
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
Wireless LAN				
1		6GK1907-0DC10-6AA3	POWER M12 CABLE CONNECTOR PRO	5)
1		6XV1870-3QH60	SIMATIC NET INDUSTRIAL ETHERNET IE TP CORD RJ45/RJ45, 6M	
Automation system				
1		6ES7654-6CL03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, SYSTEM EXPANSIONS CARD 500 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, UC 120/230V 10A POWER SUPPLY	1) 2)
		24V DC power supply	Redundant power supply	Section 16.2
Web client system				
2		6ES7658-2HX78-2YB0	SOFTWARE SIMATIC PCS 7 WEB DIAGNOSE SERVER V10.0	4)

NOTE

The laptop (web clients) hardware is not listed.

1) The number of POs can be increased later by means of extra volume licenses.

2) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

3) Wireless LAN access point with approval for the USA and Canada; approval for other countries requires a different version of W786-RJ45.

4) As an alternative to the Diagnostic licenses for servers and clients, server-based licensing can be selected for up to three web clients.

5) The selected cable is based on the architecture in which Access Point W786-1 RJ45 is powered by a separate 24V DC power source.

6) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

4. System with Multiple OS Single Stations

System with Multiple OS Single Stations

Two to five users and typically up to 1000 inputs and outputs can be supported and controlled with one SIMATIC PCS 7 system composed of several Single Stations.

In an architecture like this, the system can consist of up to 12 Single Stations. The Single Stations are configured and loaded on a central basis from an Engineering Station (ES) in a single OS project. Since the entire database is copied to all the Single Stations, the entire system can be controlled from one single location. It can be archived simultaneously on all the Single Stations. However, there is no synchronization between the single locations, and archives for alarms and tags run independently from each other.

Redundancy

With linking of a Process Historian (PH), two OS Single Stations must be set up on a redundant basis; otherwise, the link does not function. A corresponding system configuration can be found in Section [4.3](#). Two OS Single Stations can be equipped with redundancy software and hardware components to create a high-availability Operator Station. In this case, the archive synchronization is carried out between the redundant Single Stations.

The terminal bus, system bus, automation system(s) (AS) and Fieldbus can also be set up on a redundant basis. This redundancy option for the OS is limited to two OS Single Stations.

Configuration limits

OS Single Station configurations are intended for small- and medium-sized plants in the lower range. If more than two OS Single Stations are to be deployed, a Client–Server architecture is generally more economical.

By contrast with OS Servers, OS Single Stations have the following restrictions:

- Released number: 12 OS Single Stations
- Max. number of process objects per OS Single Station: 8,500 POs
- Number of measurement points per OS Single Station: approx. 4,500

Dual monitor

Each OS or ES can be expanded with the onboard standard graphics card and an appropriate adapter cable such that it is possible to connect two monitors.


The systems can be expanded with an additional Multi graphics card (2 additional monitor connections) that makes it possible to connect up to four monitors to one system.

NOTE

For more than one redundant pair of OSs, neither archive synchronization nor redundancy for alarms and process variables between one another are available.

4.1. Multiple OS Single Stations with Dual Monitor

In this configuration, the system has several OS Single Stations and one separate ES. The ES and the OS are each fitted with two monitors.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System	3)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
Operator Station				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	3)
2		6ES7658-2AA78-0YA0	SIMATIC PCS 7 OS SOFTWARE, SINGLE STATION V10.0 incl. 100 OS RUNTIME PO	1)
	2	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	

Required	Optional	Article Number	Product Description	Note
Automation system				
1		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	²⁾
		24V DC power supply	Redundant power supply	Section 16.2

NOTE


¹⁾ The number of POs can be increased later by means of extra volume licenses.

²⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

³⁾ Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

4.2. Redundant OS Single Station

In this configuration, the system has one redundant OS Single Station. The ES is configured on a separate PC.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC PCS 7 Control System IPC847E	7)
1		6GK1162-3AA00	SIMATIC NET COMMUNICATION PROCESSOR CP 1623 PCI EXPRESS	1)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
Operator Station				
2		6ES7661-1*	SIMATIC PCS 7 Control System IPC847E	7)
2		6GK1162-3AA00	SIMATIC NET COMMUNICATION PROCESSOR CP 1623 PCI EXPRESS	1)
1		6ES7652-3AA78-2YA0	SOFTWARE SIMATIC PCS 7 OS SINGLE STATION REDUNDANCY V10.0 (PO 100)	2)
2		6GK1716-0HB18-0AC0	SIMATIC NET, S7-REDCONNECT POWERPACK V18	3)
2		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	1) 5) 6)
	2	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	


Required	Optional	Article Number	Product Description	Note
Automation system				
1		6ES7654-6CL03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, SYSTEM EXPANSIONS CARD 500 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, UC 120/230V 10A POWER SUPPLY	⁴⁾
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

- ¹⁾ Necessary if a redundant system bus is selected.
- ²⁾ The number of POs can be increased later by means of extra volume licenses.
- ³⁾ Necessary if a redundant system bus or a redundant automation system is selected.
- ⁴⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).
- ⁵⁾ The onboard interfaces can be used.
- ⁶⁾ Single license for one installation.
- ⁷⁾ Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

4.3. Plain System Configuration without OS Server

For small- and medium-sized plants, implementation is possible in a very plain system configuration without an OS Server. In this case, OS single stations are used, and the number can be expanded up to a maximum of 12 single stations.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
	1	6GK1162-3AA00	SIMATIC NET COMMUNICATION PROCESSOR CP 1623 PCI EXPRESS	1)
	1	6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	1)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
Operator Station				
3		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
	3	6GK1162-3AA00	SIMATIC NET COMMUNICATION PROCESSOR CP 1623 PCI EXPRESS	1)
	3	6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	1)
1		6ES7652-3AA78-2YA0	SOFTWARE SIMATIC PCS 7 OS SINGLE STATION REDUNDANCY V10.0 (PO 100)	2)
1	5	6ES7658-2AA78-0YA0	SOFTWARE SIMATIC PCS 7 OS SINGLE STATION V10.0 (PO 100)	2)
	3	6GK1716-0HB18-0AC0	SIMATIC NET, S7-REDCONNECT POWERPACK V18	3)
	3	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	

Required	Optional	Article Number	Product Description	Note
Process Historian/Information Server				
	1	6ES7661-1*	SIMATIC Process Control System IPC847E	6)
1	1	6ES7652-7AX78-2YB0	SOFTWARE SIMATIC PCS 7 PROCESS HISTORIAN UND INFORMATION SERVER BASIC PACKAGE V10.0	
	1	6ES7652-7YA00-2YB0	SOFTWARE SIMATIC PCS 7 INFORMATION SERVER CLIENT ACCESS (1 CLIENT)	5)
Automation system				
1		6ES7654-6CL03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, SYSTEM EXPANSIONS CARD 500 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, UC 120/230V 10A POWER SUPPLY	4)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

A common (combined) system and terminal bus can be set up.

1) Necessary if a redundant bus is selected.

2) The number of POs can be increased later by means of extra volume licenses.

3) Necessary if a redundant bus or a redundant automation system is selected.

4) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available; (e.g., 24V DC or 110/230V AC).

5) The number of clients can be expanded with cumulative Information Server Client Access licenses.

6) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

5. OS Client/OS Server System

Client–Server System

Medium to large systems can benefit greatly from the SIMATIC PCS 7 Client-Server architecture. The central administration of real-time and historical values, easy entry of application changes and cost reduction are all features of SIMATIC PCS 7 systems. The basic system of a Client-Server architecture is composed of an OS Server and two or more OS Clients. The ES has a connection to both the terminal bus and the system bus, so that changes can be loaded both on the OSs and the ASs. If needed and there are no engineering tasks pending, the ES can be used as an OS Client.

Operation via server

If you operate no more than four OS Clients on one OS Server, you can use an OS Server as an operator control and monitoring station.

Redundancy

By using a redundant OS Server pair (optional redundant Process Historian), SIMATIC PCS 7 can support redundancy at all levels. This means that OS Clients accessing real-time/historical values and storage of historical data offer higher availability.

In order to guarantee increased availability on the hardware level, the system supports redundant ring structures.

Dual monitor

OS Clients can be expanded with a standard graphics card and an appropriate adapter cable such that it is possible to connect two monitors.

The systems can be expanded with an additional Multi graphics card (2 additional monitor connections) that makes it possible to connect up to four monitors to one system.

Web Server

A dedicated OS Client can be equipped with the SIMATIC PCS 7 web server software which makes possible operator control and monitoring of up to 100 web clients via the internet/Intranet. Server licensing allows more than 100 users to access one web server at the same time.


NOTE

One OS Server supports up to 40 OS Clients. The number of OS Clients in the system can be greater than 40.

The maximum number of OS Servers/OS Server pairs in a system is 18; one OS Client can be connected to a maximum of 18 OS Servers.

5.1. OS Client/OS Server with Operator Control and Monitoring on the ES and OS Server

This configuration is a system in which the ES and OS Client are used on one PC. The OS Server is configured on a separate PC.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
1		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	2)
OS Server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	


Required	Optional	Article Number	Product Description	Note
Automation system				
1		6ES7654-6CP03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1600 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	³⁾
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

- ¹⁾ The number of POs can be increased later by means of extra volume licenses.
- ²⁾ The maximum number of OS Clients when operating on the OS Server is three.
- ³⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).
- ⁴⁾ Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

5.2. OS Client/OS Server Operation on a Redundant Server Architecture

In this configuration, the system has one redundant OS Server pair, two OS Clients and one separate ES. Both OS Servers are designed as operator control and monitoring stations.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
OS Server				
2	34	6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1	17	6ES7652-3BA78-2YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER REDUNDANCY V10.0 (PO 100)	1)
		6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	


Required	Optional	Article Number	Product Description	Note
OS Client				
2		6ES7661-0*	SIMATIC Process Control System IPC647E	2) 4)
2		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	2	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Automation system				
1		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	3)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

- 1) The number of POs can be increased later by means of extra volume licenses.
- 2) The maximum number of OS Clients when operating on the OS Server is three.
- 3) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).
- 4) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

5.3. OS Client/OS Server System with a PCS 7 Web Server

In this configuration, the system has one redundant OS Server, one OS Client and one separate ES. The PCS 7 Web Server is configured on a separate PC. The PCS 7 Web Clients have separate network access to the PCS 7 Web Server.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
OS Server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)

Required	Optional	Article Number	Product Description	Note
OS Client				
1		6ES7661-0*	SIMATIC Process Control System IPC647E	4)
1		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Web Server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
1		6ES7658-2GX78-2YB0	SOFTWARE SIMATIC PCS 7 WEB SERVER BASIC V10.0	
1		6ES7658-2GF00-0XB0	SOFTWARE SIMATIC PCS 7 WEB SERVER (5 CLIENTS)	2)
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Automatisierungssystem				
1		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	3)
		24V DC power supply	Redundant power supply	Section 16.2

Note

Laptops that are used as web clients are not listed. Wireless LAN that is used for laptop connection is not listed.

1) The number of POs can be increased later by means of extra volume licenses.

2) The number of web clients can be increased later on by means of cumulative web server licenses.


3) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

4) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

5.4. OS Client/OS Server System with Terminal Server

In this configuration, the system has one redundant OS Server, one OS Client and one separate ES.

In this example, the PCS 7 Web Server and the terminal server are each configured on a separate PC. Web servers and terminal servers can also be configured on a common PC.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1 *	SIMATIC Process Control System IPC847E	4)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
OS Server				
1		6ES7661-1 *	SIMATIC Process Control System IPC847E	4)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)

Required	Optional	Article Number	Product Description	Note
OS Client				
1		6ES7661-0*	SIMATIC Process Control System IPC647E	4)
1		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Web Server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
1		6ES7658-2GX78-2YB0	SOFTWARE SIMATIC PCS 7 WEB SERVER BASIC V10.0	
1		6ES7658-2GF00-0XB0	SOFTWARE SIMATIC PCS 7 WEB SERVER (5 CLIENTS)	2)
Terminal server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	2) 4)
Automation system				
1		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	3)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

Laptops that are used as terminal clients are not listed. Wireless LAN that is used for laptop connection is not listed.

1) The number of POs can be increased later by means of extra volume licenses.


2) The number of terminal clients can be increased by means of POWERPACKs.

3) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

4) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

5.5. OS Client/OS Server System with DataMonitor Server

In this configuration, the system has one redundant OS Server, one OS Client and one separate ES. The DataMonitor Server is configured on a separate PC. Die DataMonitor Clients have access to the DataMonitor Server via a separate network.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1 *	SIMATIC Process Control System IPC847E	4)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
OS Server				
1		6ES7661-1 *	SIMATIC Process Control System IPC847E	4)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)

Required	Optional	Article Number	Product Description	Note
OS Client				
1		6ES7661-0*	SIMATIC Process Control System IPC647E	4)
1		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
DataMonitor server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	2) 4)
1		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
1		6AV6362-3AD00-0BB0	WINCC/DATAMONITOR, 3 CLIENT LICENCES (COUNTABLE), RUNTIME-SW	
Automation system				
1		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	3)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

Laptops that are used as DataMonitoring clients are not listed. Wireless LAN that is used for laptop connection is not listed.

1) The number of POs can be increased later by means of extra volume licenses.

2) Installation of the DataMonitor server:


- Restore DVD
- DataMonitor Server software
- OS Client and DataMonitor Server licenses

3) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

4) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

5.6. OS Client/OS Server with Dual Monitor

In this configuration, the system has one OS Server, two OS Clients and one separate ES. The ES and the OS Clients are each fitted with two monitors.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	3)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
OS Server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	3)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)

Required	Optional	Article Number	Product Description	Note
OS Client				
2		6ES7661-0*	SIMATIC Process Control System IPC647E	³⁾
2		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	2	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Automation system				
1		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	²⁾
		24V DC power supply	Redundant power supply	Section 16.2

NOTE


¹⁾ The number of POs can be increased later by means of extra volume licenses.

²⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

³⁾ Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

5.7. OS Client/OS Server System with Multi-User Engineering

In this configuration, the system has one OS Server and three OS Clients. One ES server and two ES clients ensure multi-user engineering.



Parts list

Required	Optional	Article Number	Product Description	Note
ES server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	3)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
ES client				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	3)
2		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	

Required	Optional	Article Number	Product Description	Note
OS Server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	3)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)
OS Client				
2		6ES7661-0*	SIMATIC Process Control System IPC647E	3)
2		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	2	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Automation system				
1		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

¹⁾ The number of POs can be increased later by means of extra volume licenses.

²⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

³⁾ Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

6. SIMATIC BATCH

SIMATIC BATCH

SIMATIC BATCH is the SIMATIC PCS 7 standard software for ISA-88 recipe management and batch management. SIMATIC BATCH is based on a scalable modular software that can be used in all SIMATIC PCS 7 architectures.

SIMATIC BATCH uses a standard Client–Server architecture with clients for recipe editing and batch control. SIMATIC BATCH clients can be installed on SIMATIC PCS 7 single stations, server/client systems and PCs, on which no further SIMATIC PCS 7 software is available.

Single Station

The smallest system that supports SIMATIC BATCH is the single station architecture. All SIMATIC BATCH software packages are installed on a single computer.

Client–Server architecture

Mid-sized systems that support multiple users and do not need redundancy are implemented as Client–Server systems. SIMATIC BATCH follows the Operator Station architecture seamlessly by distributing the BATCH server and client applications to the corresponding Operator Station computers.

Client–Server architecture (OS + SB combined)


When redundancy is required and the number of servers must be kept as low as possible, SIMATIC BATCH allows the operation of a redundant Batch server based on the redundant OS Server pair PCs.

Client–Server architecture redundant (OS + SB-Server separated)

When it comes to large, high-performance applications, the SIMATIC PCS 7 Client–Server architecture allows the distribution of applications across multiple PCs. In this case, the BATCH server and OS Server run on two independent PCs. Each of them can be implemented on a redundant basis, as a result of which a very high level of availability is achieved. The OS Client PCs can run the BATCH client application and access both the OS Server and the BATCH server. If necessary, the OS Client and BATCH client application can run on separate PCs as well.

6.1. SIMATIC BATCH Single Station

This configuration is a system where ES, OS, BATCH Server, and BATCH Client (BATCH Control Center) and BATCH Recipe Editor are used on one PC as a Single Station. The BATCH client must be installed and configured in addition to the BATCH server.



Parts list


Required	Optional	Article Number	Product Description	Note
Engineering Station, Operator Station, BATCH Server and BATCH Client				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7651-5AA78-0YA0	SIMATIC PCS 7, SOFTWARE, ES SINGLE STATION V10.0 (AS/OS: PO 250)	1)
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
1		6ES7657-0UX78-0YB0	SOFTWARE SIMATIC BATCH SINGLE STATION PACKAGE V10.0	
1		6ES7657-0XA00-0YB0	SOFTWARE SIMATIC BATCH (1 UNITS)	3)
Automation system				
1		6ES7654-6CL03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, SYSTEM EXPANSIONS CARD 500 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

- ¹⁾ The number of POs can be increased later by means of extra volume licenses.
- ²⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).
- ³⁾ The number of batch units can be increased by means of cumulative batch unit licenses. The number of units is project-dependent.
- ⁴⁾ Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

6.2. SIMATIC BATCH Single Station in an OS Client/OS Server Architecture

In this example configuration, the system has two OS Clients and two OS Servers (the number of OS Clients and OS Servers may vary). The BATCH Single Station is configured as a single station on a separate PC and may also include the BATCH client installation.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
OS Server				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)

Required	Optional	Article Number	Product Description	Note
OS Client				
2		6ES7661-0*	SIMATIC Process Control System IPC647E	4)
2		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	2	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
BATCH Single Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7657-0UX78-0YB0	SOFTWARE SIMATIC BATCH SINGLE STATION PACKAGE V10.0	
1		6ES7657-0XA00-0YB0	SOFTWARE SIMATIC BATCH (1 UNIT)	3)
Automation system				
2		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

1) The number of POs can be increased later by means of extra volume licenses.


2) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

3) The number of batch units can be increased by means of cumulative batch unit licenses. The number of units is project-dependent.

4) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

6.3. SIMATIC BATCH OS Client/OS Server

This example configuration is a system with three BATCH clients installed on the OS Clients and a separate ES. The OS Server and BATCH server are integrated on a common PC.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	5)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
OS Server, BATCH Server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	5)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)
1		6ES7657-0TX78-0YB0	SOFTWARE SIMATIC BATCH SERVER V10.0	
1		6ES7657-0XB00-0YB0	SOFTWARE SIMATIC BATCH (10 UNITS)	3)

Required	Optional	Article Number	Product Description	Note
OS Client, BATCH Client				
3		6ES7661-0*	SIMATIC Process Control System IPC647E	5)
3		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	3	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
3		6ES7657-0VX78-0YB5	SOFTWARE SIMATIC BATCH CLIENT V10.0	
1	2	6ES7657-0A78-0YB5	SOFTWARE SIMATIC BATCH RECIPE SYSTEM V10.0	4)
Automation system				
2		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

¹⁾ The number of POs can be increased later by means of extra volume licenses.

²⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).


³⁾ The number of batch units can be increased by means of cumulative batch unit licenses. The number of units is project-dependent.

⁴⁾ The SIMATIC BATCH recipe system license is needed on at least one of the clients in a Client–Server System (on all the clients that are to be used to create and edit recipes).

⁵⁾ Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

6.4. Separate SIMATIC BATCH Server

In this example configuration, the system has two OS Clients and two OS Servers, two BATCH clients and two OS Servers. The BATCH Server is configured on a separate PC.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	5)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
OS Server				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	5)
2		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)
BATCH server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	5)
1		6ES7657-0TX78-0YB0	SOFTWARE SIMATIC BATCH SERVER V10.0	
1		6ES7657-0XB00-0YB0	SOFTWARE SIMATIC BATCH (10 UNITS)	3)


Required	Optional	Article Number	Product Description	Note
OS Client				
2		6ES7661-0*	SIMATIC Process Control System IPC647E	5)
2		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	2	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Batch client				
2		6ES7661-0*	SIMATIC Process Control System IPC647E	5)
2		6ES7657-0VX78-0YB5	SOFTWARE SIMATIC BATCH CLIENT V10.0	
1	1	6ES7657-0AX78-0YB5	SOFTWARE SIMATIC BATCH RECIPE SYSTEM V10.0	4)
Automation system				
2		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

- 1) The number of POs can be increased later by means of extra volume licenses.
- 2) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).
- 3) The number of batch units can be increased by means of cumulative batch unit licenses. The number of units is project-dependent.
- 4) The SIMATIC BATCH recipe system license is needed on at least one of the clients in a Client–Server System (on all the clients that are to be used to create and edit recipes).
- 5) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

6.5. Redundant SIMATIC BATCH Client-Server Architecture

This example configuration is a system with a redundant BATCH server pair and two BATCH clients, which are installed together with the OS Clients on one computer. The ES is configured on a separate PC. The terminal bus and the system bus are also set up on a redundant basis.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	9)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
1		6GK1162-3AA00	SIMATIC NET COMMUNICATION PROCESSOR CP 1623 PCI EXPRESS	1)
1		6GK1716-0HB18-0AC0	SIMATIC NET, S7-REDCONNECT POWERPACK V18	3)
1		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	8)
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	


Required	Optional	Article Number	Product Description	Note
OS Server, BATCH Server				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	9)
1		6ES7652-3BA78-2YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER REDUNDANCY V10.0 (PO 100)	2)
2		6GK1162-3AA00	SIMATIC NET COMMUNICATION PROCESSOR CP 1623 PCI EXPRESS	1)
2		6GK1716-0HB18-0ACO	SIMATIC NET, S7-REDCONNECT POWERPACK V18	3)
2		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	8)
2		A5E02639550	DESKTOP ADAPTER NETWORK CARD	6)
1		6XV1870-3RH60	SIMATIC NET INDUSTRIAL ETHERNET TP XP CORD RJ45/RJ45, 6M	
2		6ES7657-0TX78-0YB0	SOFTWARE SIMATIC BATCH SERVER V10.0	
2		6ES7657-0XB00-0YB0	SOFTWARE SIMATIC BATCH (10 UNITS)	5)
OS Client, BATCH Client				
2		6ES7661-0*	SIMATIC Process Control System IPC647E	9)
2		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
2		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	8)
	2	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
2		6ES7657-0VX78-0YB5	SOFTWARE SIMATIC BATCH CLIENT V10.0	
1	1	6ES7657-0AX78-0YB5	SOFTWARE SIMATIC BATCH RECIPE SYSTEM V10.0	7)
Automation system				
2		6ES7656-6CN33-1CF0	SIMATIC PCS 7 REDUNDANCY AS, 2X CPU 410-5H, 2 DP-MODULE, 2X PROFINET-IO, SYSTEM EXPANSION CARD 1000 PO, AS RT PO 100, 2 X 2 10M SYNC-MODULE AND 2 X 1M FO, 2 X CP443-1	4)
		24V DC power supply	Redundant power supply	Section 16.2

Note

- 1) Needed if a redundant system bus is chosen.
- 2) The number of POs can be increased later by means of extra volume licenses.
- 3) Necessary if a redundant system bus or a redundant automation system is chosen.
- 4) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).
- 5) The number of batch units can be increased by means of cumulative batch unit licenses. The number of units is project-dependent.
- 6) Additional network adapters are required for redundancy switching.
- 7) The SIMATIC BATCH recipe system license is needed on at least one of the clients in a Client–Server System (on all the clients that are to be used to create and edit recipes).
- 8) The onboard interfaces can be used.
- Single License for one installation. Necessary if a redundant terminal bus is selected.
- 9) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

6.6. SIMATIC BATCH Client-Server Architecture Redundant (OS + SB Server Separated)

In this example configuration, the system has one redundant BATCH server pair and two redundant OS Server pairs. The five SIMATIC BATCH clients are combined with the five OS Clients. This ES is a separate PC.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	7)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
OS Server				
4		6ES7661-1*	SIMATIC Process Control System IPC847E	7)
4		6GK1716-0HB18-0AC0	SIMATIC NET, S7-REDCONNECT POWERPACK V18	1)
2		6ES7652-3BA78-2YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER REDUNDANCY V10.0 (PO 100)	2)

Required	Optional	Article Number	Product Description	Note
BATCH server				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	7)
2		A5E02639550	DESKTOP ADAPTER NETWORK CARD	5)
1		6XV1870-3RH60	SIMATIC NET INDUSTRIAL ETHERNET TP XP CORD RJ45/RJ45, 6M	
2		6ES7657-0TX78-0YB0	SOFTWARE SIMATIC BATCH SERVER V10.0	
2		6ES7657-0XB00-0YB0	SOFTWARE SIMATIC BATCH (10 UNITS)	4)
OS Client, BATCH Client				
5		6ES7661-0*	SIMATIC Process Control System IPC647E	7)
5		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	5	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
2	3	6ES7657-0VX78-0YB5	SOFTWARE SIMATIC BATCH CLIENT V10.0	
1	4	6ES7657-0AX78-0YB5	SOFTWARE SIMATIC BATCH RECIPE SYSTEM V10.0	6)
Automation system				
2		6ES7656-6CQ33-1CF0	SIMATIC PCS 7 REDUNDANCY AS, 2X CPU 410-5H, 2 DP-MODULE, 2X PROFINET-IO, SYSTEM EXPANSION CARD 2k+ PO, AS RT PO 100, 2 X 2 10M SYNC-MODULE AND 2 X 1M FO, 2 X CP443-1 IE/PN, 1 X UR2-H ALU RACK, 2 X UC 120/230V 10A RED. POWER SUPPLY	3)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

- 1) Needed for a redundant automation system.
- 2) The number of POs can be increased later by means of extra volume licenses.
- 3) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).
- 4) The number of batch units can be increased by means of cumulative BATCH unit licenses. The number of units is project-dependent.
- 5) The second network adapter is used for redundancy switching.
- 6) The SIMATIC BATCH recipe system license is needed on at least one of the clients in a Client–Server System (on all the clients that are to be used to create and edit recipes).
- 7) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

7. SIMATIC Route Control

SIMATIC Route Control

SIMATIC Route Control is an optional package of the SIMATIC PCS 7 process control system and is integrated into the PCS 7 engineering and runtime system. Route Control is a system for automatic or manual control of material transport (routes) in process plants.

Simple transport processes right up to comprehensive route combinations are possible at runtime. System operators only need to specify the source and target locations for the route request. Route Control allows users to determine, check, control and monitor transport routes and the route elements they contain.

Single Station

The smallest system that supports all SIMATIC Route Control functions is the Single Station.

Route Control engineering, server, client and the functionality of the automation system are all installed on one PC and run in-parallel with the operator station.

Client-Server architecture

Mid-sized systems that support multiple users and require no redundancy are implemented as Client–Server systems. SIMATIC Route Control scales seamlessly to the Operator Station architecture by distributing the Route Control server and client applications to the corresponding Operator station PCs.

Client-Server architecture redundant (OS + RCS combined)


When redundancy is required and the number of servers must be kept as small as possible, SIMATIC Route Control allows the operation of a redundant Route Control server based on the redundant OS Server pair.

Client-Server architecture redundant (OS + RCS separated)

For large and high-performance applications, the SIMATIC PCS 7 Client–Server architecture allows the distribution of applications across multiple PCs. In this case, the Route Control Server and OS Server run on two independent PCs. Each of them can be configured redundantly, as a result of which high level of availability is achieved. The OS Client PCs can access both the OS Server and the Route Control server. If necessary, both the OS Client and the Route Control client application can run on separate PCs.

7.1. SIMATIC Route Control Single Station

This configuration is a system in which the ES, OS and Route Control Server are used on one PC as a single station.



Parts list


Required	Optional	Article Number	Product Description	Note
Engineering Station, Operator Station and Route Control Server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7651-5AA78-0YA0	SIMATIC PCS 7, SOFTWARE, ES SINGLE STATION V10.0 (AS/OS: PO 250)	1)
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
1		6ES7658-7DX78-0YB5	SOFTWARE SIMATIC ROUTE CONTROL ENGINEERING V10.0	
1		6ES7658-7FX78-0YB0	SOFTWARE SIMATIC ROUTE CONTROL SERVER V10.0	
1		6ES7658-7FF00-0XB0	SOFTWARE SIMATIC ROUTE CONTROL (10 ROUTES)	3)
1		6ES7658-7EX78-0YB5	SOFTWARE SIMATIC ROUTE CONTROL CENTER V10.0	
Automation system				
1		6ES7654-6CL03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, SYSTEM EXPANSIONS CARD 500 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

- ¹⁾ The number of POs can be increased later by means of extra volume licenses.
- ²⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).
- ³⁾ At least one SIMATIC Route Control Routes license (for sets of 10/50) is required per project. The number of routes can be increased at a later stage with cumulative SIMATIC Route Control Routes Licenses.
- ⁴⁾ Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

7.2. SIMATIC Route Control Client-Server Architecture

In this example configuration, the system has three Route Control clients and one separate ES. The OS Server and the Route Control Server are integrated on one PC.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
1		6ES7658-7DX78-0YB5	SOFTWARE SIMATIC ROUTE CONTROL ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
OS Server, Route Control Server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)
1		6ES7658-7FX78-0YB0	SOFTWARE SIMATIC ROUTE CONTROL SERVER V10.0	
1		6ES7658-7FF00-0XB0	SOFTWARE SIMATIC ROUTE CONTROL (10 ROUTES)	3)

Required	Optional	Article Number	Product Description	Note
OS Client, Route Control client				
3		6ES7661-0*	SIMATIC Process Control System IPC647E	4)
3		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	3	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
3		6ES7658-7EX78-0YB5	SOFTWARE SIMATIC ROUTE CONTROL CENTER V10.0	
Automation system				
2		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

1) The number of POs can be increased later by means of extra volume licenses.


2) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

3) At least one SIMATIC Route Control Routes license (for sets of 10/50) is required per project. The number of routes can be increased at a later stage with cumulative SIMATIC Route Control Routes Licenses.

4) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

7.3. Redundant SIMATIC Route Control Client/ServerArchitecture

In this example configuration, the system has one redundant Route Control server pair and two Route Control clients. The ES is configured on a separate PC. The terminal bus and the system bus are also set up on a redundant basis.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	10)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
1		6GK1162-3AA00	SIMATIC NET COMMUNICATION PROCESSOR CP 1623 PCI EXPRESS	1)
1		6GK1716-0HB18-0AC0	SIMATIC NET, S7-REDCONNECT POWERPACK V18	3)
1		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	7) 8) 9)
1		6ES7658-7DX78-0YB5	SOFTWARE SIMATIC ROUTE CONTROL ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	


Required	Optional	Article Number	Product Description	Note
OS Server, Route Control Server				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	10)
1		6ES7652-3BA78-2YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER REDUNDANCY V10.0 (PO 100)	2)
2		6GK1162-3AA00	SIMATIC NET COMMUNICATION PROCESSOR CP 1623 PCI EXPRESS	1)
2		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCES	7) 8) 9)
2		6GK1716-0HB18-0AC0	SIMATIC NET, S7-REDCONNECT POWERPACK V18	3)
2		A5E02639550	DESKTOP ADAPTER NETWORK CARD	6)
1		6XV1870-3RH60	SIMATIC NET INDUSTRIAL ETHERNET TP XP CORD RJ45/RJ45, 6M	
2		6ES7658-7FX78-0YB0	SOFTWARE SIMATIC ROUTE CONTROL SERVER V10.0	
2		6ES7658-7FF00-0XB0	SOFTWARE SIMATIC ROUTE CONTROL (10 ROUTES)	5)
OS Client, Route Control client				
2		6ES7661-0*	SIMATIC Process Control System IPC647E	10)
2		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	7) 8) 9)
2		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	2	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
2		6ES7658-7EX78-0YB5	SOFTWARE SIMATIC ROUTE CONTROL CENTER V10.0	
Automation system				
2		6ES7656-6CN33-1CF0	SIMATIC PCS 7 REDUNDANCY AS, 2X CPU 410-5H, 2 DP-MODULE, 2X PROFINET-IO, SYSTEM EXPANSION CARD 1000 PO, AS RT PO 100, 2 X 2 10M SYNC-MODULE AND 2 X 1M FO, 2 X CP443-1	4)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

- 1) Needed if a redundant system bus is chosen.
- 2) The number of POs can be increased later by means of extra volume licenses.
- 3) Necessary if a redundant system bus or a redundant automation system is chosen.
- 4) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).
- 5) At least one SIMATIC Route Control Routes license (for sets of 10/50) is required per Route Control Server. The number of routes can be increased at a later stage with cumulative SIMATIC Route Control Routes Licenses.
- 6) Additional network adapters are required for redundancy switching.
- 7) The onboard interfaces can be used.
- 8) Single license for one installation.
- 9) Necessary if a redundant terminal bus is selected.
- 10) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

7.4. SIMATIC Route Control Client/Server Architecture Redundant (OS + RCS Server Separated)

In this example configuration, the system has one redundant Route Control server pair and two redundant OS Server pairs. The five Route Control clients are combined with the five OS Clients. The ES is configured on a separate PC.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
1		6ES7658-7DX78-0YB5	SOFTWARE SIMATIC ROUTE CONTROL ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
OS Server				
4		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
4		6GK1716-0HB18-0AC0	SIMATIC NET, S7-REDCONNECT POWERPACK V18	1)
2		6ES7652-3BA78-2YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER REDUNDANCY V10.0 (PO 100)	2)

Required	Optional	Article Number	Product Description	Note
Route Control Server				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
2		A5E02639550	DESKTOP ADAPTER NETWORK CARD	5)
1		6XV1870-3RH60	SIMATIC NET INDUSTRIAL ETHERNET TP XP CORD RJ45/RJ45, 6M	
2		6GK1716-0HB18-0AC0	SIMATIC NET, S7-REDCONNECT POWERPACK V18	1)
2		6ES7658-7FX78-0YB0	SOFTWARE SIMATIC ROUTE CONTROL SERVER V10.0	
2		6ES7658-7FF00-0XB0	SOFTWARE SIMATIC ROUTE CONTROL (10 ROUTES)	4)
OS Client, Route Control client				
5		6ES7661-0*	SIMATIC Process Control System IPC647E	6)
5		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	5	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
5		6ES7658-7EX78-0YB5	SOFTWARE SIMATIC ROUTE CONTROL CENTER V10.0	
Automation system				
2		6ES7656-6CQ33-1CF0	SIMATIC PCS 7 REDUNDANCY AS, 2X CPU 410-5H, 2 DP-MODULE, 2X PROFINET-IO, SYSTEM EXPANSION CARD 2k+ PO, AS RT PO 100, 2 X 2 10M SYNC-MODULE AND 2 X 1M FO, 2 X CP443-1 IE/PN, 1 X UR2-H ALU RACK, 2 X UC 120/230V 10A RED. POWER SUPPLY	3)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

1) Required for redundant automation system.

2) The number of POs can be increased later by means of extra volume licenses.

3) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

4) At least one SIMATIC Route Control Routes license (for sets of 10/50) is required per Route Control Server. The number of routes can be increased at a later stage with cumulative SIMATIC Route Control Routes Licenses.

5) Additional network adapters are required for redundancy switching.

6) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

8. SIMATIC Route Control and SIMATIC BATCH

For BATCH applications that need transparent material transportation between subsystems, SIMATIC PCS 7 supports the integration of SIMATIC BATCH and SIMATIC Route Control into a single system. The ISA-88-based recipe management and batch processing software SIMATIC BATCH integrates seamlessly with Route Control and allows material transport to be controlled via the recipe functions in the control recipe. Both SIMATIC BATCH and Route Control can be used for systems that range from starter size up to distributed Client–Server architectures.

Using SIMATIC BATCH and SIMATIC Route Control in a single system, it is possible to implement the following configurations:

Single Station

The smallest system is the single-user architecture. All software packages (server/client/engineering) of OS, SIMATIC BATCH and Route Control are installed on a single computer.

Client–Server architecture

Mid-sized systems that support multiple users and do not need redundancy are implemented as Client–Server systems. SIMATIC BATCH and SIMATIC Route Control use the OS architecture by utilizing the BATCH and Route Control server/client applications on the corresponding OS PCs.


Client–Server architecture redundant (OS + SB+RCS combined)

When redundancy is required and the number of servers must be kept as small as possible, SIMATIC BATCH and SIMATIC Route Control can be used on the basis of redundant OS Servers (a combination of three redundant functions on two servers).

Client–Server architecture redundant (OS + SB and RCS separated)

When it comes to large, high-performance applications, the SIMATIC PCS 7 client/server architecture allows the distribution of applications across multiple PCs. In this case, the BATCH server, Route Control server and OS Server run on independent PCs. Each of them can be configured redundantly, as a result of which high level of availability is achieved. The OS Client PCs can be installed together with the BATCH and Route Control Client applications and can therefore access the OS Server as well as the BATCH and Route Control server. If necessary, the OS Client, Route Control client and BATCH client application can run on separate PCs as well.

The Figure below shows a sample configuration with three OS Clients/Route Control clients/BATCH clients. The OS Server, Route Control Server, and the BATCH Server are integrated on one PC. This ES is a separate PC.



9. Archiving

SIMATIC PCS 7 digital preservation

Archiving of data for analysis purposes where the system collects large amounts of data over long periods is supported by the Process Historian. The Process Historian collects the archive data from the OS Servers or OS Single Stations. Batch data can also be archived on the Process Historian. These archive data can be visualized directly on OS Clients or Single Stations.

The information server can be used to display these data in reports. For long-term archiving, archive data from the Process Historian can be stored on external media (backup drives). If the exported data is required at a later point in time for the purpose of the analysis, these can be restored on the Process Historian.

Client–Server system

The Process Historian always runs on a separate PC.

The choice of hardware depends on the system configuration and archiving load of the Process Historian. The PH-HWAdvisor software tool can be used to determine the correct Process Historian hardware for a given PCS 7 quantity structure.

NOTE

The PH-HWAdvisor can be downloaded free of charge in the entry "Determination of suitable hardware for the Process Historian with the 'PH-HWAdvisor' tool":
<https://support.industry.siemens.com/cs/ww/en/view/109740115>

NOTE

For PCS 7 configuration limits with one OS Server, up to four OS Clients, an archive load of up to 1500 variable(s) and 10 alarms/min, an IPC 847E can be used as the hardware basis for a Process Historian.

The operation of a combined Process Historian/Information Server on an IPC 847E is not recommended.

More information on hardware requirements can be found in the "Process Historian" manual in the "Process Historian – Installation Notes" Section:
<https://support.industry.siemens.com/cs/ww/en/view/109825371>

All OS Clients can retrieve data from the Process Historian. From the perspective of the OS Client, there is no difference between access to data of the OS Server or data of the Process Historian.

Redundant OS Server Pair with a Single Process Historian

If redundant OS operation is required and constant online availability of archive data is not mandatory, a single Process Historian can be connected to a redundant OS Server pair. The OS Servers also have a local short-term archive.

Information Server


The Information Server is the reporting system of the Process Historian. Based on the Microsoft Reporting Services, it offers web-based thin-client access to the historical data. Add-ins for Microsoft Word and Excel provide additional access to the database of the Process Historian. The Information Server can be installed and operated on the Process Historian hardware or on separate hardware. An OS Client version of the SIMATIC PCS 7 Industrial Workstation is suitable for the separate Information Server.

NOTE

When selecting the information server computer hardware, please note the hardware requirements in the "Information Server" manual in the "Information Server – Installation Notes" Section:
<https://support.industry.siemens.com/cs/ww/en/view/109825366>

9.1. OS Client/OS Server

In this configuration, the system has one OS Server and two OS Clients. The ES and Process Historian/information server are each configured on a separate PC.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	5)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
OS Server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	5)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1) 3)
Process Historian/Information Server				
1			DETERMINATION OF THE HARDWARE USING THE PH-HWAdvisor	
1		6ES7652-7AX78-2YB0	SOFTWARE SIMATIC PCS 7 PROCESS HISTORIAN UND INFORMATION SERVER BASIC PACKAGE V10.0	
1		6ES7652-7YA00-2YB0	SOFTWARE SIMATIC PCS 7 INFORMATION SERVER CLIENT ACCESS (1 CLIENT)	4)

Required	Optional	Article Number	Product Description	Note
OS Client				
2		6ES7661-0*	SIMATIC Process Control System IPC647E	5)
2		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	2	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Automation system				
2		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

1) The number of POs can be increased later by means of extra volume licenses.

2) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).


3) The tag inventory can be expanded to up to 120,000 archive tags using cumulative SIMATIC PCS 7 OS/PH Archive volume licenses.

4) The number of clients can be expanded with cumulative Information Server Client Access licenses.

5) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

9.2. Redundant OS Server Pair and Process Historian

In this configuration, the system has one redundant OS Server pair and two OS Clients. The ES and Process Historian/information server are each configured on a separate PC. The terminal bus and the system bus are set up on a redundant basis.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering System				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	11)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
1		6GK1162-3AA00	SIMATIC NET COMMUNICATION PROCESSOR CP 1623 PCI EXPRESS	1)
1		6GK1716-0HB18-0AC0	SIMATIC NET, S7-REDCONNECT POWERPACK V18	3)
1		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	7) 8) 9)
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	

Required	Optional	Article Number	Product Description	Note
OS Server				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	11)
1		6ES7652-3BA78-2YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER REDUNDANCY V10.0 (PO 100)	2)
2		6GK1162-3AA00	SIMATIC NET COMMUNICATION PROCESSOR CP 1623 PCI EXPRESS	1)
2		6GK1716-0HB18-0ACO	SIMATIC NET, S7-REDCONNECT POWERPACK V18	3)
2		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	7) 8) 9)
Process Historian/Information Server				
1			DETERMINATION OF THE HARDWARE USING THE PH-HWAdvisor.	10)
1		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	7) 8) 9)
1		6ES7652-7AX78-2YB0	SOFTWARE SIMATIC PCS 7 PROCESS HISTORIAN UND INFORMATIONEN SERVER BASIC PACKAGE V10.0	
1		6ES7652-7AX78-2YB0	SOFTWARE SIMATIC PCS 7 INFORMATION SERVER CLIENT ACCESS 1 CLIENT	6)
OS Client				
2		6ES7661-0*	SIMATIC Process Control System IPC647E, Core i5-8500, ES/OS Single Station, OS Client, 480 GB SSD 2.5 SATA, 8 GB DDR4 SDRAM, PCS 7 V10.0, Windows 10 Enterprise 2019 LTSC 64BIT	11)
2		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	7) 8) 9)
2		6AV6881-0AU14-0AA0	USB KEYBOARD TKL-105 GERMAN	
2		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	2	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Automation system				
2		6ES7656-6CN33-1CF0	SIMATIC PCS 7 REDUNDANCY AS, 2X CPU 410-5H, 2 DP-MODULE, 2X PROFINET-IO, SYSTEM EXPANSION CARD 1000 PO, AS RT PO 100, 2 X 2 10M SYNC-MODULE AND 2 X 1M FO, 2 X CP443-1	4)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

- 1) Needed if a redundant system bus is chosen.
- 2) The number of POs can be increased later by means of extra volume licenses.
- 3) Necessary if a redundant system bus or a redundant automation system is chosen.
- 4) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).
- 5) The tag inventory can be expanded to up to 120,000 archive tags using cumulative SIMATIC PCS 7 OS Archive volume licenses.
- 6) The number of clients can be expanded with cumulative Information Server Client Access licenses.
- 7) The onboard interfaces can be used.
- 8) Single license for one installation.
- 9) Necessary if a redundant terminal bus is selected.
- 10) This configuration requires hardware with two network adapters.
- 11) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

10. Fieldbus

PROFIBUS DP/PROFIBUS PA/FOUNDATION Fieldbus/PROFINET Fieldbus

SIMATIC PCS 7 enables the connection of different fieldbus technologies through flexible architectures and seamless integration. In this connection, the process devices can be connected to the automation system either via PROFINET or PROFIBUS DP.

PROFINET is based on the international standards IEC 61158 and IEC 61784 and combines the advantages of the open network standard Industrial Ethernet and PROFIBUS fieldbus system.

With PROFINET, a large number of devices at the field level can communicate at a speed of up to 100 Mbps. Within a network, the number of devices is almost unlimited. Up to 250 devices can be connected per PROFINET interface of the automation system.

Directly connected PROFINET devices, such as decentralized peripherals and drives, as well as PROFIBUS DP compact devices and PROFIBUS PA process devices integrated via the IE/PB Link are supported as devices.

PROFINET offers countless possibilities for networking these devices in the system with line, ring, tree and star topologies. In order to reduce the planning effort and eliminate possible sources of error, PROFINET Blueprints provide tested, scalable network configurations. These are tailored to typical system configurations of process automation and are recommended as prepared solution approaches or standard blocks for planning PROFINET networks.

NOTE

The PROFINET Blueprints and further information on the integration of PROFINET in SIMATIC PCS 7 can be found in the application example "PROFINET in Process Automation with SIMATIC PCS 7":
<https://support.industry.siemens.com/cs/ww/en/view/72887082>

The PROFIBUS DP, based on the robust RS-485 technology, is a proven fieldbus that supports reliable data exchange with up to 125 slaves per network. SIMATIC PCS 7 automation systems are equipped with the PROFIBUS DP Master functionality and can be extended to several PROFIBUS DP networks.

Repeaters increase expansion of the PROFIBUS network across multiple isolated segments and also the number of possible stations to a maximum of 125 slaves. If diagnostics functions for physical cable diagnostics are desired in addition to the standard repeater functionality, a diagnostics repeater can be used as an alternative. It monitors the copper bus cables in online mode. In the event of an error, it sends a diagnostic message with detailed information about the type and location of the fault to the PROFIBUS DP Master.

Intelligent field devices based on the PROFIBUS PA and FOUNDATION Fieldbus H1 standards can be integrated in SIMATIC PCS 7 by connecting them directly to the PROFIBUS DP via dedicated gateways (e.g. PA Link and Compact FF Link). In addition to data transmission, the PROFIBUS PA and FOUNDATION Fieldbus H1 field devices are fed via the bus.

NOTE

Further information on the integration of FOUNDATION Fieldbus H1 (FF) in SIMATIC PCS 7 can be found in the application example "Configuration of FOUNDATION Fieldbus H1 (FF) with SIMATIC PCS 7":
<https://support.industry.siemens.com/cs/ww/en/view/64329637>

DP/PA couplers, PA Link and Compact FF Link components act as network transitions between the PROFIBUS DP networks and the PA/FF side supplied via bus. This means that a larger number of PROFIBUS PA slaves and FF field devices can be used without overloading the existing PROFIBUS DP address space.

Intrinsically-safe components for PROFIBUS DP, PROFIBUS PA and FOUNDATION Fieldbus H1 make it possible to use field devices directly in an environment at risk from explosions.

Optical PROFIBUS DP

To implement greater distances and to achieve ring error tolerance and electrical isolation, PROFIBUS DP allows the use of fiber-optic network components. The optical PROFIBUS DP can be set up as a simple line or fault-tolerant ring. Both design variants are possible for both the individual and redundant PROFIBUS DP fieldbus.

Redundant electrical PROFIBUS DP, PROFIBUS PA and FOUNDATION Fieldbus H1

If a high level of availability is required, PROFIBUS DP supports the setup of redundant networks for the connection of IO Racks, DP/PA and FF Links by using an H System. A redundant PROFIBUS DP network consists of two separate electrical lines which are connected to the two PROFIBUS masters of the H System and several redundant DP slaves. The PA Link and FF Compact FF Link gateways provide the opportunity to build the field device bus PROFIBUS PA or FOUNDATION Fieldbus H1 as a fault-tolerant ring, thereby increasing the availability of the complete field device network. The redundant PROFIBUS PA is available in combination with individual and redundant PROFIBUS DP networks. The redundant FOUNDATION Fieldbus H1 is available when using the Compact FF Link with redundant PROFIBUS DP.

Electrical and optical PROFINET

PROFINET enables the use of electrical and optical cables as a transmission medium. Optical cables offer, for example, advantages in terms of EMC load and make it possible to bridge longer distances, whereas electrical cables are cheaper and less sensitive to mechanical influences. Both transmission media can be used in combination and are suitable for point-to-point connections as well as for the setup of MRP rings.

Redundancy concepts for the PROFINET fieldbus

PROFINET provides two redundancy concepts for increasing the availability of PROFINET devices

This includes setting up ring topologies using the Media Redundancy Protocol (MRP) and connecting the devices to high-availability automation systems via system redundancy. Both concepts are independent of each other and can be used separately or combined.

The Media Redundancy Protocol (MRP) is defined in the IEC 62439 standard and allows ring topologies with up to 50 stations. All stations must support the media redundancy with MRP.

In functional condition, the redundancy manager (a predefined station of the ring) opens the ring and therefore ensures loop-free communication. If the transmission path in the ring is interrupted at one point, e. g. by disconnecting the ring line or failure of a station, the redundancy manager immediately closes the ring and, as a result, provides an alternative communication path. The maximum reconfiguration time is 200 ms.

When connecting devices to high-availability automation systems, a distinction is made between two variants:

- Simple S2 system redundancy: Each device has an interface module that establishes a connection to both controllers of the H System
- Redundant PROFINET configuration R1: Each device has two interface modules, each of which establishes a connection to a controller of the H system.
- The advantage of the redundant PROFINET configuration R1 is that the level of availability of the IO devices is increased through the two interface modules and communication via two separate PROFINET networks (subnetworks).


NOTE

Further information on the structure of ring topologies with MRP as well as on simple and redundant PROFINET configurations can be found in the application example "PROFINET in Process Automation with SIMATIC PCS 7":

<https://support.industry.siemens.com/cs/ww/en/view/72887082>

10.1. DP-PA/DP-FF Fieldbus

In this configuration, the system has PROFIBUS DP, PROFIBUS PA, and FOUNDATION Fieldbus. The network transitions are implemented with DP/PA Link or Compact FF Link.



Parts list

Required	Optional	Article Number	Product Description	Note
Automation system				
1		6ES7654-6CL03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, SYSTEM EXPANSIONS CARD 500 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, UC 120/230V 10A POWER SUPPLY	1)
		24V DC power supply	Redundant power supply	Section 16.2
ET 200M				
1		6ES7153-2BA10-0XB0	SIMATIC DP, ET 200M INTERFACE IM 153-2 HIGH FEATURE FOR MAX. 12 S7-300 MODULES	2) 3)
1		6ES7195-7HA00-0XA0	SIMATIC DP, BUS UNIT FOR ET200M	
1		6ES7195-7HB00-0XA0	SIMATIC DP, BUS UNIT FOR ET200M F. THE INTEGR.OF TWO 40 MM WIDE I/O SUBMODULES	4)
DIAGNOSTICS REPEATER				
	1	6ES7972-0AA02-0XA0	SIMATIC DP, RS485 DIAGNOSTICS REPEATER	2)
DP/PA LINK				
1		6ES7153-2BA70-0XB0	SIMATIC DP, INTERFACE DP/PA-LINK A. ET200M IM153-2 HF	2) 5)
1		6ES7157-0AC85-0XA0	SIMATIC DP, FIELD DEVICE LINK DP/PA COUPLER FDC 157-0 NON EX-VERSION	6)
1		6ES7195-7HA00-0XA0	SIMATIC DP, BUS UNIT FOR ET200M F. THE INTEGR.OF 1 PS A.1 IM153	
1		6ES7195-7HF80-0XA0	SIMATIC DP, BUS UNIT BM DP/PA FOR EXPANDED TEMPERATURE RANGE SUBMODULE FOR DP/PA COUPLER	
1		6ES7157-0AG81-0XA0	ACT. FIELD DISTRIBUTOR AFD FOR PROFIBUS PA RING	
Compact FF LINK				
1		6ES7658-3MD88-0YA5	SOFTWARE SIMATIC PDM PCS 7-FF V9.3 (100 TAGS)	7)
1		6ES7655-5BA00-0AB0	SIMATIC COMPACT FF LINK COMBINATION OF DP/FF LINK AND FF COUPLER	2) 8)
SIMOCODE				
1		3UF7010-1AB00-0	BASIC UNIT SIMOCODE pro V PB PRO V	

NOTE

¹⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

Notes regarding PROFIBUS DP:

The maximum number of PROFIBUS DP slaves per master is 125 (typically 30–80)

The maximum number of slaves per segment is 32 (including repeater and master), segments are separated from (diagnostics) repeaters

²⁾ ET 200M, DP/PA Link, Diagnostic Repeater and Compact FF Link require power supply for 24V DC.

³⁾ Additionally, signal modules are required for the connection of process signals. Type and number depend on the individual requirements.

⁴⁾ Type and number of bus modules depend on the signal modules used.

⁵⁾ Max. of 64 field devices per DP/PA Link

⁶⁾ Notes regarding FDC 157-0:

Max. of 5 FDC 157-0 DP/PA couplers in a DP/PA link

Max. of 31 field devices per FDC 157-0. (typically 20–25)

The maximum current supplied from FDC 157-0 is 1,000 mA

The maximum PA segment length is 1,900 m (typically 500–1000 m)

⁷⁾ With an existing PDM V9.3 license that includes routing, only one additional license is needed for FF communication. You can find this optional license in the PCS 7 catalog.

⁸⁾ Notes regarding Compact FF Link.


Max. of 31 field devices per FF segment. (typically 8–12)

Max. Power supplied by Compact FF Link, 500mA

The maximum FF segment length is 1,900 m (typically 500–1000 m)

10.2. Single Optical DP-PA/DP-FF Fieldbus

This configuration is an optical PROFIBUS DP system with four optical link modules. The optical part of the PROFIBUS DP system can be set up as a simple line or as a ring. The network transitions are implemented with DP/PA Link or Compact FF Link.



Parts list

Required	Optional	Article Number	Product Description	Note
Automation system				
1		6ES7654-6CL03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, SYSTEM EXPANSIONS CARD 500 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, UC 120/230V 10A POWER SUPPLY	1)
		24V DC power supply	Redundant power supply	Section 16.2
OPTICAL FIELDBUS				
4		6GK1503-3CB00	PROFIBUS OLM/G12 V4.0 OPTICAL LINK MODULE	2)
ET 200M				
1		6ES7153-2BA10-0XB0	SIMATIC DP, ET 200M INTERFACE IM 153-2 HIGH FEATURE FOR MAX. 12 S7-300 MODULES	3) 4)
1		6ES7195-7HA00-0XA0	SIMATIC DP, BUS UNIT FOR ET200M	
1		6ES7195-7HB00-0XA0	SIMATIC DP, BUS UNIT FOR ET200M F. THE INTEGR.OF TWO 40 MM WIDE I/O SUBMODULES	5)
DP/PA LINK				
1		6ES7153-2BA70-0XB0	SIMATIC DP, INTERFACE DP/PA-LINK A. ET200M IM153-2 HF	3) 6)
1		6ES7157-0AC85-0XA0	SIMATIC DP, FIELD DEVICE LINK DP/PA COUPLER FDC 157-0 NON EX-VERSION	7)
1		6ES7195-7HA00-0XA0	SIMATIC DP, BUS UNIT FOR ET200M F. THE INTEGR.OF 1 PS A.1 IM153	
1		6ES7195-7HF80-0XA0	SIMATIC DP, BUS UNIT BM DP/PA FOR EXPANDED TEMPERATURE RANGE SUBMODULE FOR DP/PA COUPLER	
1		6ES7157-0AG81-0XA0	ACT. FIELD DISTRIBUTOR AFD FOR PROFIBUS PA RING	
Compact FF LINK				
1		6ES7658-3MD88-0YA5	SOFTWARE SIMATIC PDM PCS 7-FF V9.3 (100 TAGS)	8)
1		6ES7655-5BA00-0AB0	SIMATIC COMPACT FF LINK COMBINATION OF DP/FF LINK AND FF COUPLER	3) 9)
SIMOCODE				
1		3UF7010-1AB00-0	BASIC UNIT SIMOCODE pro V PB PRO V	

NOTE

¹⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

Notes regarding PROFIBUS DP:

- The maximum number of PROFIBUS DP slaves per master is 125 (typically 30–80)
- The maximum number of slaves per segment is 32 (including repeater and master), segments are separated from (diagnostics) repeaters
- ²⁾ OLM/G12 establishes a fault-tolerant PROFIBUS DP ring. OLM/G12 needs a 24V DC power supply.

³⁾ ET 200M, DP/PA Link, Diagnostic Repeater and Compact FF Link require power supply for 24VDC.

⁴⁾ Additionally, signal modules are required for the connection of process signals. Type and number depend on the individual requirements.

⁵⁾ Type and number of bus modules depend on the signal modules used.

⁶⁾ Max. of 64 field devices per DP/PA Link

⁷⁾ Notes regarding FDC 157-0:

Max. of 5 FDC 157-0 DP/PA couplers in a DP/PA link

Max. of 31 field devices per FDC 157-0. (typically 20–25)

The maximum current supplied from FDC 157-0 is 1,000 mA

The maximum PA segment length is 1,900 m (typically 500–1000 m)

⁸⁾ With an existing PDM V9.3 license that includes routing, only one additional license is needed for FF communication. You can find this optional license in the PCS 7 catalog.

⁹⁾ Notes regarding Compact FF Link.


Max. of 31 field devices per FF segment. (typically 8–12)

Max. Power supplied by Compact FF Link, 500mA

The maximum FF segment length is 1,900 m (typically 500–1000 m)

10.3. Redundant DP-PA/DP-FF Fieldbus

This configuration is a redundant PROFIBUS DP system. The network transitions are also redundant with two DP/PA links or Compact FF links each.



Parts list

Required	Optional	Article Number	Product Description	Note
Automation system				
1		6ES7656-6CL33-1CF0	SIMATIC PCS 7 REDUNDANCY AS, 2X CPU 410-5H, 2 DP-MODULE, 2X PROFINET-IO, SYSTEM EXPANSION CARD 500 PO, AS RT PO 100, 2 X 2 10M SYNC-MODULE AND 2 X 1M FO, 2 X CP443-1 IE/PN, 1 X UR2-H ALU RACK, 2 X UC 120/230V 10A RED. POWER SUPPLY	1)
	2	6GK7443-5DX05-0XE0	COMMUNICATION PROCESSOR CP443-5 EXTENDED	2)
		24V DC power supply	Redundant power supply	Section 16.2
ET 200M				
2		6ES7153-2BA10-0XB0	SIMATIC DP, ET 200M INTERFACE IM 153-2 HIGH FEATURE FOR MAX. 12 S7-300 MODULES	3) 4)
1		6ES7195-7HD10-0XA0	SIMATIC DP, BUS UNIT FOR ET200M FOR INTEGRATING 2 IM153-2 RED.	
1		6ES7195-7HB00-0XA0	SIMATIC DP, BUS UNIT FOR ET200M F. THE INTEGR.OF TWO 40 MM WIDE I/O SUBMODULES	5)

Required	Optional	Article Number	Product Description	Note
Y LINK				
1		6ES7197-1LA12-0XA0	SIMATIC S7-400H, Y-LINK FOR CONNECTING SINGLE-CHANNEL DP SLAVES TO S7-400H AND AS 410H	3)
DIAGNOSTICS REPEATER				
	2	6ES7972-0AA02-0XA0	SIMATIC DP, RS485 DIAGNOSTICS REPEATER	3)
DP/PA LINK				
2		6ES7153-2BA70-0XB0	SIMATIC DP, INTERFACE DP/PA-LINK A. ET200M IM153-2 HF	6)
2		6ES7157-0AC85-0XA0	SIMATIC DP, FIELD DEVICE LINK DP/PA COUPLER FDC 157-0 NON EX-VERSION	7)
1		6ES7195-7HD80-0XA0	SIMATIC DP, BUS UNIT BM IM 157 FOR EXPANDED TEMPERATURE RANGE	
1		6ES7195-7HG80-0XA0	SIMATIC DP, BUS COUPLE BM DP/PA FOR 2 FDC 157-0 FOR REDUNDANT OPERATION	
2		6ES7157-0AG81-0XA0	ACT. FIELD DISTRIBUTOR AFD FOR PROFIBUS PA RING	
1		6ES7157-0AG80-1XA1	10 protective caps for the unused connections on AFD	
Compact FF LINK				
1		6ES7658-3MD88-0YA5	SOFTWARE SIMATIC PDM PCS 7-FF V9.3 (100 TAGS)	8)
1		6ES7655-5EF00-0AA0	SIMATIC DP, BUS MODULE FOR INTEGRATING OF 2 COMPACT FF LINK IN REDUNDANT OPERATION	
2		6ES7655-5BA00-0AB0	SIMATIC COMPACT FF LINK COMBINATION OF DP/FF LINK AND FF COUPLER	3) 9)
2		6ES7157-0AG81-0XA0	ACTIVE FIELD DISTRIBUTOR AFD4 FOR FF RING	
SIMOCODE				
1		3UF7010-1AB00-0	BASIC UNIT SIMOCODE pro V PB PRO V	

NOTE

¹⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

²⁾ Notes regarding CP443-5 Extended:

- The maximum number of PROFIBUS DP slaves per master is 125 (typically 30–80)
- The maximum number of slaves per segment is 32 (including repeater and master), segments are separated from (diagnostics) repeaters

³⁾ ET 200M, DP/PA Link, Y LINK diagnostic repeater and Compact FF Link require a 24V DC power supply.

⁴⁾ Additionally, signal modules are required for the connection of process signals. Type and number depend on the individual requirements.

⁵⁾ Type and number of bus modules depend on the signal modules used.

⁶⁾ Max. of 64 field devices per DP/PA Link

⁷⁾ Notes regarding FDC 157-0:

- Max. of one pair of redundant FDC 157-0s per DP/PA link and 3 single FDC 157-0
- Max. of 31 field devices per redundant pair of FDC 157-0 (typically 20–25)
- The maximum current supplied from FDC 157-0 is 1,000 mA
- The maximum PA segment length is 1,900 m (typically 500–1000 m)

⁸⁾ With an existing PDM V9.3 license that includes routing, only one additional license is needed for FF communication. You can find this optional license in the PCS 7 catalog.

⁹⁾ Notes regarding Compact FF Link:


Max. of 31 field devices per FF segment. (typically 8–12)

Max. Power supplied by Compact FF Link, 500mA

The maximum FF segment length is 1,900 m (typically 500–1000 m)

10.4. Redundant Optical DP-PA/DP-FF Fieldbus

This configuration is a redundant, optical PROFIBUS DP system with optical link modules. The network transitions are also redundant with two DP/PA links or Compact FF links each.



Parts list

Required	Optional	Article Number	Product Description	Note
Automation system				

Required	Optional	Article Number	Product Description	Note
1		6ES7656-6CL33-1CF0	SIMATIC PCS 7 REDUNDANCY AS, 2X CPU 410-5H, 2 DP-MODULE, 2X PROFINET-IO, SYSTEM EXPANSION CARD 500 PO, AS RT PO 100, 2 X 2 10M SYNC-MODULE AND 2 X 1M FO, 2 X CP443-1 IE/PN, 1 X UR2-H ALU RACK, 2 X UC 120/230V 10A RED. POWER SUPPLY	1)
	2	6GK7443-5DX05-0XE0	COMMUNICATION PROCESSOR CP443-5 EXTENDED	2)
		24V DC power supply	Redundant power supply	Section 16.2
OPTICAL FIELDBUS				
10		6GK1503-3CB00	PROFIBUS OLM/G12 V4.0 OPTICAL LINK MODULE	8)
ET 200M				
2		6ES7153-2BA10-0XB0	SIMATIC DP, ET 200M INTERFACE IM 153-2 HIGH FEATURE FOR MAX. 12 S7-300 MODULES	3) 4)
1		6ES7195-7HD10-0XA0	SIMATIC DP, BUS UNIT FOR ET200M FOR INTEGRATING 2 IM153-2 RED.	
1		6ES7195-7HB00-0XA0	SIMATIC DP, BUS UNIT FOR ET200M F. THE INTEGR.OF TWO 40 MM WIDE I/O SUBMODULES	5)
Y LINK				
2		6ES7197-1LA11-0XA0	SIMATIC S7-400H, Y-LINK FOR CONNECTING SINGLE-CHANNEL DP SLAVES TO S7-400H	3)
DP/PA LINK				
2		6ES7153-2BA70-0XB0	SIMATIC DP, INTERFACE DP/PA-LINK A. ET200M IM153-2 HF	3) 6)
2		6ES7157-0AC85-0XA0	SIMATIC DP, FIELD DEVICE LINK DP/PA COUPLER FDC 157-0 NON EX-VERSION	7)
1		6ES7195-7HD80-0XA0	SIMATIC DP, BUS UNIT BM IM 157 FOR EXPANDED TEMPERATURE RANGE	
1		6ES7195-7HG80-0XA0	SIMATIC DP, BUS COUPLE BM DP/PA FOR 2 FDC 157-0 FOR REDUNDANT OPERATION	
2		6ES7157-0AG81-0XA0	ACT. FIELD DISTRIBUTOR AFD FOR PROFIBUS PA RING	
1		6ES7157-0AG80-1XA1	10 protective caps for the unused connections on AFD	
Compact FF LINK				
1		6ES7658-3MD88-0YA5	SOFTWARE SIMATIC PDM PCS 7-FF V9.3 (100 TAGS)	8)
1		6ES7655-5EF00-0AA0	SIMATIC DP, BUS MODULE FOR INTEGRATING OF 2 COMPACT FF LINK IN REDUNDANT OPERATION	
2		6ES7655-5BA00-0AB0	SIMATIC COMPACT FF LINK COMBINATION OF DP/FF LINK AND FF COUPLER	3) 9)
2		6ES7157-0AG81-0XA0	ACTIVE FIELD DISTRIBUTOR AFD4 FOR FF RING	
SIMOCODE				
		3UF7010-1AB00-0	BASIC UNIT SIMOCODE pro V PB PRO V	

NOTE

¹⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

²⁾ Notes regarding CP443-5 Extended:

- The maximum number of PROFIBUS DP slaves per master is 125 (typically 30–80)
- The maximum number of slaves per segment is 32 (including repeater and master), segments are separated from (diagnostics) repeaters

³⁾ ET 200M, DP/PA Link, Y LINK diagnostic repeater and Compact FF Link require a 24V DC power supply.

⁴⁾ Additionally, signal modules are required for the connection of process signals. Type and number depend on the individual requirements.

⁵⁾ Type and number of bus modules depend on the signal modules used.

⁶⁾ Max. of 64 field devices per DP/PA Link

⁷⁾ Notes regarding FDC 157-0:

- Max. of one pair of redundant FDC 157-0s per DP/PA link and 3 single FDC 157-0
- Max. of 31 field devices per redundant pair of FDC 157-0 (typically 20–25)
- The maximum current supplied from FDC 157-0 is 1,000 mA
- The maximum PA segment length is 1,900 m (typically 500–1000 m)

⁸⁾ With an existing PDM V9.3 license that includes routing, only one additional license is needed for FF communication. You can find this optional license in the PCS 7 catalog.

⁹⁾ Notes regarding Compact FF Link:


Max. of 31 field devices per FF segment. (typically 8–12)

Max. Power supplied by Compact FF Link, 500mA

The maximum FF segment length is 1,900 m (typically 500–1000 m)

10.5. PROFINET Fieldbus with a Standard Automation System

This configuration is a standard automation system with PROFINET, PROFIBUS DP and PROFIBUS PA. The gateway to PROFIBUS DP is realized with IE/PB LINK PN IO. The integration of the PROFIBUS PA field devices via the Compact Field Unit PA.



Parts list

Required	Optional	Article Number	Product Description	Note
Automation system				
1		6ES7654-6CL03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, SYSTEM EXPANSIONS CARD 500 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, UC 120/230V 10A POWER SUPPLY	1) 2)
		24V DC power supply	Redundant power supply	Section 16.2
ET 200SP HA				
1		6DL1155-6AU00-OPM0	INTERFACEMODUL IM 155-6 PN HA	3) 4)
1		6DL1193-6BH00-OSM0	SUBRACK MODULE (INTERFACE MODULE – SINGLE)	
1		6DL1193-6GA00-ONN0	SUBRACK MODULE 2x	5)
1		6DL1193-6TP00-ODH1	TERMINALBLOCK (SINGLE)	5)
1		6DL1193-6PA00-0AA0	SERVERMODUL	
1		6DL1193-6AF00-0AA0	PROFINET-BUSADAPTER FAST CONNECT	6)
Compact Field Unit				
1		6ES7655-5PX11-0XX0	COMPACT FIELD UNIT PA	3)
1		6DL1193-6AF00-0AA0	PROFINET-BUSADAPTER FAST CONNECT	6)
Gateway to PROFIBUS				

Required	Optional	Article Number	Product Description	Note
1		6GK1411-5AB10	IE/PB LINK PN IO	3) 7)
SIMOCODE				
1		3UF7011-1AB00-0	SIMOCODE pro V PN	

NOTE

¹⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

It is not possible to operate PROFINET networks on the external Ethernet CP443-1.

²⁾ Max. of 250 devices per onboard CPU interface.

³⁾ IM 155-6, Compact Field Unit PA and IE/PB LINK PN IO require power supply for 24V DC.

⁴⁾ Additionally, signal modules are required for the connection of process signals. Type and number depend on the individual requirements.

⁵⁾ Type and number of subrack modules and terminal blocks depend on the signal modules used.

⁶⁾ Alternatively, bus adapters can be used for optical connection via fiber-optic cables

⁷⁾ Only compact devices are supported as PROFIBUS DP stations and lower-level PROFIBUS PA nodes (PA couplers).

NOTE

In the configuration above, the network topology has not been taken into account, as it depends among other things on the number of devices and local conditions.


Recommended and tested topologies can be found as PROFINET blueprints in the application example "PROFINET in Process Automation with SIMATIC PCS 7":

<https://support.industry.siemens.com/cs/ww/en/view/72887082>

10.6. PROFINET Fieldbus with a High-Availability Automation System - Simple System Redundancy S2

This configuration is a high-availability automation system with PROFINET. To increase the availability of the devices, the PROFINET network is set up as an open ring.

Connecting to a closed ring with MRP is also possible, but would have more disadvantages than advantages, since the reconfiguration of the MRP ring is slower, among other things, than the switching time of the H System in cases error.



Parts list

Required	Optional	Article Number	Product Description	Note
Automation system				
1		6ES7656-6CL33-1CF0	SIMATIC PCS 7 REDUNDANCY AS, 2X CPU 410-5H, 2 DP-MODULE, 2X PROFINET-IO, SYSTEM EXPANSION CARD 500 PO, AS RT PO 100, 2 X 2 10M SYNC-MODULE AND 2 X 1M FO, 2 X CP443-1	1) 2) 3)
		24V DC power supply	Redundant power supply	Section <u>16.2</u>
ET 200SP HA				
1		6DL1155-6AU00-0PM0	INTERFACEMODUL IM 155-6 PN HA	4) 5)
1		6DL1193-6BH00-0SM0	SUBRACK MODULE (INTERFACE MODULE – SINGLE)	
1		6DL1193-6GA00-0NN0	Subrack module 2x	6)
1		6DL1193-6TP00-0DH1	TERMINALBLOCK (SINGLE)	6)
1		6DL1193-6PA00-0AA0	SERVERMODUL	
1		6DL1193-6AF00-0AA0	PROFINET-BUSADAPTER FAST CONNECT	8)
Compact Field Unit				
1		6ES7655-5PX11-0XX0	COMPACT FIELD UNIT PA	4)
1		6DL1193-6AF00-0AA0	PROFINET-BUSADAPTER FAST CONNECT	8)
ET 200M				
1		6ES7153-4BA00-0XB0	SIMATIC DP, ET 200M INTERFACE IM 153-4 PN IO HIGH FEATURE FOR MAX. 12 S7-300 MODULES	4) 5)
1		6ES7195-7HA00-0XA0	SIMATIC DP, BUS UNIT FOR ET 200M	
1		6ES7195-7HB00-0XA0	SIMATIC DP, BUS UNIT FOR ET 200M F. THE INTEGR.OF TWO 40 MM WIDE I/O SUBMODULES	7)
Gateway to PROFIBUS				
1		6GK1411-5BB00	IE/PB LINK HA	4) 9)
SIMOCODE				
1		3UF7011-1AB00-0	SIMOCODE pro V PN	


NOTE

- ¹⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).
It is not possible to operate PROFINET networks on the external Ethernet CP443-1.
- ²⁾ Only devices that support system redundancy S2 can be operated redundantly on the H System. Devices that do not support system redundancy can only be assigned to one H CPU.
- ³⁾ Max. of 250 devices per onboard CPU interface.
- ⁴⁾ ET 200SP HA, ET 200M, Compact Field Unit PA and IE/PB LINK HA required a power supply for 24V DC.
- ⁵⁾ Additionally, signal modules are required for the connection of process signals. Type and number depend on the individual requirements.
- ⁶⁾ Type and number of subrack modules and terminal blocks depend on the signal modules used.
- ⁷⁾ Type and number of bus modules depend on the signal modules used.
- ⁸⁾ Alternatively, bus adapters can be used for optical connection via fiber-optic cables
- ⁹⁾ Only compact devices are supported as PROFIBUS DP nodes and lower-level PROFIBUS PA stations (PA couplers).

10.7. Redundant PROFINET Fieldbus with a High-Availability Automation System - R1

This configuration is a high-availability automation system with a redundant PROFINET configuration R1. In this configuration, the automation system, network and interface modules are configured redundantly in order to achieve the highest possible level of availability when connecting the decentralized peripherals.

Optionally, the peripheral modules of the ET 200SP HA can also be provided with redundant peripheral modules. Counter-rotating cabling is used. This ensures that all other nodes remain available in the event of a failure or station replacement.



Parts list

Required	Optional	Article Number	Product Description	Note
Automation system				
1		6ES7656-6CL33-1CF0	SIMATIC PCS 7 REDUNDANCY AS, 2X CPU 410-5H, 2 DP-MODULE, 2X PROFINET-IO, SYSTEM EXPANSION CARD 500 PO, AS RT PO 100, 2 X 2 10M SYNC-MODULE AND 2 X 1M FO, 2 X CP443-1	1) 2) 3) 4)
		24V DC power supply	Redundant power supply	Section <u>16.2</u>
ET 200SP HA				
6		6DL1155-6AU00-0PM0	INTERFACEMODUL IM 155-6 PN HA	5) 6)
3		6DL1193-6BH00-0RM0	SUBRACK MODULE (INTERFACE MODULE – REDUNDANT)	
3		6DL1193-6GA00-0NN0	Subrack module 2x	7)
3		6DL1193-6TP00-0DH1	TERMINALBLOCK (SINGLE)	7)
3		6DL1193-6PA00-0AA0	SERVERMODUL	
6		6DL1193-6AF00-0AA0	PROFINET-BUSADAPTER FAST CONNECT	8)

NOTE

1) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

It is not possible to operate PROFINET networks on the external Ethernet CP443-1.

2) Only devices that support at least system redundancy S2 can be operated redundantly on the H-System. Devices that do not support system redundancy can only be assigned to one H CPU.

3) Max. of 64 R1 devices per onboard CPU interface. In combination with S2-Devices a maximum of 250 per CPU onboard interface.

4) An additional license is required for connecting R1 devices.

5) ET 200SP HA needs a 24V DC power supply.

6) Additionally, signal modules are required for the connection of process signals. Type and number depend on the individual requirements.

7) Type and number of subrack modules and terminal blocks depend on the signal modules used.

8) Alternatively, bus adapters can be used for optical connection via fiber-optic cables

NOTE

The choice of network topology depends, among other things, on the number of devices and local conditions.
Recommended and tested topologies can be found as PROFINET blueprints in the application example "PROFINET in Process Automation with SIMATIC PCS 7":

<https://support.industry.siemens.com/cs/ww/en/view/72887082>

11. SIMATIC PDM

SIMATIC PDM

SIMATIC PDM is a universal tool for parameterization, diagnostics, commissioning, servicing and maintenance of field devices. Furthermore, the Maintenance Station displays the PDM diagnostic data of field devices.

PDM is fully integrated in the SIMATIC PCS 7 Engineering System.

SIMATIC PDM V9.3 supports communication with devices on PROFINET, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus H1, and HART (ET 200M, ET200SP HA, or ET200iSP modules, modem, RS 232).

The open technologies EDDL (Electronic Device Description Language) and FDI (Field Device Integration) are used to integrate these devices.

Note In the respective PDM delivery release information, you will find a list of devices supported by a PDM version and profiles.

SIMATIC PDM supports stand-alone operation and can be integrated into STEP 7/PCS 7.

PDM is installed in the Engineering System of medium to large system configurations, with or without a redundant server, and connected to field devices over the Ethernet system bus and the routing functionality of the automation system.

Local service and parameterization stations on the fieldbus

PDM can also be used for stand-alone operation. The stand-alone version is used on a standard computer without STEP 7 or PCS 7 installation. This computer is connected to the PROFINET or PROFIBUS DP fieldbus. This configuration allows you to carry out parameterization and maintenance tasks for HART, PROFIBUS PA, PROFIBUS DP and PROFINET. PROFIBUS DP/PA devices can be accessed from the LifeList.

HART devices can be accessed via ET200 modules, HART modems (point-to-point) or HART Multiplexers.

Local service and parameterization stations on the system bus

With SIMATIC PDM on a Field PG, you can use the routing functionality to access the field devices directly from the system bus and perform maintenance, service, and parameterization tasks. The Field PG is particularly suitable for rugged day-to-day industrial use due to its robust construction.

Single-user system (Single Station)

When using a single station, PDM connects to field devices via the Ethernet system bus and the routing functionality of the automation system. When using multi-Engineering Systems, PDM must be installed on all Engineering Systems where PDM is used.

Non-SIMATIC S7 master

Non-PCS 7 PROFIBUS DP Masters can use the Ethernet/PROFINET to PROFIBUS DP (IE/PB Link) interfaces, which allow a seamless connection to lower-level field devices. By integrating PDM into STEP 7, more field devices can be managed comprehensively and their data can be archived and versioned just like in SIMATIC PCS 7.


SIMATIC PDM Server Option

This option licenses and enables the following applications:

- Access to SIMATIC PDM functions via a web browser. The connection from the PDM-Client PC is only possible with Internet Explorer V10, V11 or Chrome.
- Access with a maintenance client to the SIMATIC PDM parameterization interface for the selected field device. The call is carried out via the PDM button in the Maintenance Faceplate.

11.1. Local Service and Parameterization Station on the Fieldbus

In this configuration, the system has one laptop and SIMATIC PDM in stand-alone operation. The field devices are connected by means of PROFINET or PROFIBUS.



Parts list

Required	Optional	Article Number	Product Description	Note
Laptop PDM				
	1	6GK1571-0BA00-0AA0	SIMATIC S7, PC ADAPTER USB NETWORK CARD	1)
	1	6GK1561-2AA00	CP5612 COMMUNICATION PROCESSOR PCI CARD (32 BIT / 64 BIT)	1)
1		6ES7658-3AB88-0YA5	SOFTWARE SIMATIC PDM BASIC V9.3 (4 TAGs)	2)
	1	6ES7658-3NX88-2YB5	SIMATIC PDM Extended V9.3	
	1	6ES7658-3TX88-2YB5	SIMATIC PDM Server V9.3	
	1	6ES7658-3UA00-2YB5	SIMATIC PDM 1 CLIENT	3)
	1	6ES7658-7BX61-0YA0	SIMATIC LOGON SERVICE V1.6	

NOTE

The SIMATIC PCS 7 single station is not listed.

1) USB network adapter for laptop use. Use CP5612 (or other approved network adapters) for desktop PC systems.


Only for connection to the PROFIBUS DP fieldbus.

2) The number of TAGs can be increased by means of cumulative TAG licenses.

3) The total number of PDM client licenses can be increased up to 30.

11.2. Local Service and Parameterization Station on the System Bus

In this configuration, the system has one Field PG and SIMATIC PDM in stand-alone operation. Field devices on PROFINET or PROFIBUS networks are connected via S7-CPU and a system bus.



Parts list

Required	Optional	Article Number	Product Description	Note
Laptop PDM				
1		6ES7658-3JD88-0YA5	SOFTWARE SIMATIC PDM SERVICE V9.3 (50 TAGs)	1)
1		6ES7658-3CX88-2YB5	SOFTWARE SIMATIC PDM ROUTING V9.3	
	1	6ES7658-3NX88-2YB5	SIMATIC PDM EXTENDED V9.3	
	1	6ES7658-3TX88-2YB5	SIMATIC PDM SERVER V9.3	
	1	6ES7658-3UA00-2YB5	SIMATIC PDM 1 CLIENT	2)
	1	6ES7658-7BX61-0YA0	SIMATIC LOGON SERVICE V1.6	


NOTE

1) The number of TAGs can be increased by means of cumulative TAG licenses.

2) The total number of PDM client licenses can be increased up to 30.

11.3. SIMATIC PDM and PCS 7 Single Station

This configuration is a system in which the ES, OS, and PDM are used on one PC as a single station. The connection to the field devices is made by means of the system bus.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station, PDM and Operator Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	7)
1		6ES7651-5AA78-0YA0	SIMATIC PCS 7, SOFTWARE, ES SINGLE STATION V10.0 (AS/OS: PO 250)	1)
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
1		6ES7658-3LD88-0YA5	SOFTWARE SIMATIC PDM PCS 7 V9.3 (100 TAGs)	3)
	1	6ES7658-3QX88-2YB5	SOFTWARE SIMATIC PDM COMMUNICATION FOUNDATION FIELD BUS V9.3	4)
	1	6ES7658-3TX88-2YB5	SIMATIC PDM SERVER V9.3	
	1	6ES7658-3UA00-2YB5	SIMATIC PDM 1 CLIENT	6)
Automation system				
1		6ES7654-6CL03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, SYSTEM EXPANSIONS CARD 500 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, UC 120/230V 10A POWER SUPPLY	2) 5)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

1) The number of POs can be increased later by means of extra volume licenses.

2) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

3) The number of TAGs can be increased by means of cumulative TAG licenses.

4) Optional for FOUNDATION Fieldbus communication


5) The following applies to each Standard CPU/CPU PN: If you use the PROFIBUS DP interface of the CPU for data record routing, you must configure this CPU in the HW Config with firmware V5.1 or higher. If this is not the case, it needs a CP443-5 Ext PROFIBUS communications module to use PDM data record routing.

6) The number of PDM client licenses can be increased up to 30 in total.

7) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

11.4. SIMATIC PDM and PCS 7 OS Client/OS Server System

In this configuration, the system has one OS Server and three OS Clients. The ES and the SIMATIC PDM are configured on a separate PC.




Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	7)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
1		6ES7658-3LD88-0YA5	SOFTWARE SIMATIC PDM PCS 7 V9.3 (100 TAGs)	3)
	1	6ES7658-3QX88-2YB5	SOFTWARE SIMATIC PDM Communication FOUNDATION FIELD BUS V9.3	4)
	1	6ES7658-3TX88-2YB5	SIMATIC PDM SERVER V9.3	
	1	6ES7658-3UA00-2YB5	SIMATIC PDM 1 CLIENT	6)
OS Server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	7)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)
OS Client				
3		6ES7661-0*	SIMATIC Process Control System IPC647E	7)
3		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	3	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Automation system				
2		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	2) 5)
		24V DC power supply	Redundant power supply	Section 16.2

11.5. SIMATIC PDM and Non-SIMATIC S7 Master

This configuration is a PC with SIMATIC PDM (stand-alone) connected to a PROFIBUS or PROFINET field device segment of a non-SIMATIC S7 master or S7 controller (without data set routing functionality).

PROFIBUS DP is connected to PDM via a gateway (IE/PB-Link), while PROFINET networks are connected to PDM via the service bridge and therefore remain logically separated from each other.



Parts list

Required	Optional	Article Number	Product Description	Note
PDM (Alternative 1)				
1		6ES7658-3AB88-0YA5	SIMATIC PDM BASIC V9.3 INCL. 4 TAGS	2)
	1	6ES7658-3NX88-2YB5	SIMATIC PDM EXTENDED V9.3	
PDM (Alternative 2)				
	1	6ES7658-3JD88-0YA5	SIMATIC PDM Service V9.3 INCL. 54 TAGs	2)
	1	6ES7658-3NX88-2YB5	SIMATIC PDM EXTENDED V9.3	

Required	Optional	Article Number	Product Description	Note
PDM (Alternative 3)				
1		6ES7658-3TX88-0YA5	SIMATIC PDM stand-alone server V9.3 PRODUCT PACKAGE FOR SERVICE AND DEVICE MANAGEMENT IN SUBSYSTEMS WITH - SIMATIC PDM BASIC INCL. 4 TAGS - SIMATIC PDM EXTENDED - SIMATIC PDM SERVER - 2 X SIMATIC PDM 1 CLIENT (100 TAGS)	2)
Further options for PDM alternatives 1 and 2				
	1	6ES7658-3TX88-2YB5	SIMATIC PDM Server V9.3	
	1	6ES7658-3UA00-2YB5	SIMATIC PDM 1 Client	3)
System bus				
1		6GK1411-5AB00	IE/PB-Link PN IO	1)
1		6GK5208-0BA00-2AC2	SCALANCE XC208 manageable Layer 2 IE switch; 8x 10/100 Mbit/s RJ45 ports; 1x console port; diagnostic LED; redundant power supply	1) 4)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

1) The IE/PB module and XC switch require a 24V DC power supply.

2) The number of PDM TAGs can be increased by means of cumulative TAG licenses.

3) The total number of PDM client licenses can be increased up to 30..


4) SCALANCE XC208 is configured as a service bridge. For the configuration file, see the entry "Service Bridge – Setting-up and Configuration":

<https://support.industry.siemens.com/cs/ww/en/view/109747975>

11.6. SIMATIC PDM Stand-Alone Server

With the SIMATIC PDM Stand alone Server product package, you can establish central service and parameterization stations that operate according to the Client–Server principle. These can be set up on an independent system, an Engineering System or on the SIMATIC PCS 7 Maintenance Station.

When used on the Maintenance Station, the device parameters can be accessed from any SIMATIC PCS 7 Maintenance Station client to selected field devices via the PDM parameterization interface.



Parts list

Required	Optional	Article Number	Product Description	Note
PDM Server				
1		6ES7658-3TX88-0YA5	SIMATIC PDM STAND-ALONE SERVER V9.3 PRODUCT PACKAGE FOR SERVICE AND DEVICE MANAGEMENT IN SUBSYSTEMS WITH - SIMATIC PDM BASIC INCL. 4 TAGS - SIMATIC PDM EXTENDED - SIMATIC PDM SERVER - 2 X SIMATIC PDM 1 CLIENT (100 TAGS)	1)
1		6ES7658-3CX88-2YB5	SOFTWARE SIMATIC PDM ROUTING V9.3	
PDM Client				
3		6ES7658-3UA00-2YB5	SIMATIC PDM 1 CLIENT	2)
Automation system				
2		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	3) 4)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

Laptops that are used as PDM clients are not listed. Wireless LAN that is used for laptop connection is not listed.

1) The number of PDM TAGs can be increased by means of cumulative TAG licenses.

2) The total number of PDM client licenses can be increased up to 30..

3) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

4) The following applies to each Standard CPU/CPU PN:

If you use the PROFIBUS DP interface of the CPU for data record routing, you must configure this CPU in the HW Config with firmware V5.1 or higher.

If this is not the case, it needs a CP443-5 Ext PROFIBUS communications module to use PDM data record routing.

12. Maintenance Station (Asset Management)

The Maintenance Station implements Plant Asset Management (according to NAMUR NE 129) in a PCS 7 multi-project. That is, a system for maintaining the value of process Engineering Systems using information about the condition of all system components (assets).

For this purpose, the Maintenance Station provides you with comprehensive diagnostic and maintenance information at all times. It is fully integrated in the Operator System and contains all system information.

The diagnostics screens that are structured according to the process cell hierarchy with the operating states of the SIMATIC PCS 7 components can be displayed on the SIMATIC PCS 7 Maintenance Station and also on the OS clients. More detailed diagnostic information that has also been determined by SIMATIC PDM is displayed in the faceplates of these stations. However, enhanced online diagnostic functions in conjunction with HW Config can only be accessed via a PCS 7 Maintenance Station on the ES.

Versions

The Maintenance Station is available in the following three versions:

1. SIMATIC PCS 7 Maintenance Station Basis (integrated in the PCS 7 project) License-free version with functional limitations
2. SIMATIC PCS 7 Maintenance Station Standard (integrated in the PCS 7 project) Licensed version with all functions
3. SIMATIC PDM Maintenance Station 2.0 (stand-alone project)
Separate station based on bundle installation (Microbox PC). In the following referred to as PDM Maintenance Station

The possible configurations for the two variants of the PCS 7 Maintenance Station are described in the Sections [12.1](#) to [12.5](#).

The configuration of the PDM Maintenance Station is described in Section [12.6](#).

Single station

The ES, OS and asset management functions are connected to the single station via the Ethernet system bus. Asset Management provides diagnostic and maintenance data of the automation system, PC station, active networking components and all of the connected field devices.

Client–Server (single/redundant)

Like the PCS 7-OS, the Maintenance Station can be used in a decentralized Client–Server structure in SIMATIC PCS 7. The maintenance server is based on an OS Server. It can be implemented as a combined OS/MS server (on an existing OS Server) or as a separate MS server.

The Maintenance Station uses the standard display and messages from the PCS 7-OS that refer to the diagnosis area.

The OS Clients that are logged on to the MS server can access maintenance screens in PCS 7 just like standard process screens.

These maintenance screens include additional information for detailed diagnostics and troubleshooting of intelligent field devices.

Furthermore, SIMATIC PDM can be called from any of these MS clients.

Maintenance Station in flat hierarchies

The PCS 7 Maintenance Station can also be used in flat hierarchies.

SIMATIC PDM Maintenance Station

The SIMATIC PDM MS is a pre-configured single station as IPC Mircobox 427E. It is designed for stand-alone use and independent of the automation solution used.

In terms of representation and function, the SIMATIC PDM MS is designed in the same way as a SIMATIC PCS 7 Maintenance Station. All operating and monitoring functions are carried out locally on this PC station.


Primarily, SIMATIC PDM MS is designed to be used for diagnostics, field device management, acquiring and transferring the parameterization, diagnostic, and status data of field devices.

NOTE

There is exactly one MS server for each project (single or redundant).
Alternatively, several PDM Maintenance Stations can be used in one project.

12.1. PCS 7 Maintenance Station in Single Station

This configuration is a system in which the ES, OS, and Maintenance Station are used on one PC as a single station.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station, PDM and Operator Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
1		6ES7651-5AA78-0YA0	SIMATIC PCS 7, SOFTWARE, ES SINGLE STATION V10.0 (AS/OS: PO 250)	1)
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-3LD88-0YA5	SOFTWARE SIMATIC PDM PCS 7 V9.3 (100 TAGs)	3)
1		6ES7658-7GB78-0YB0	SOFTWARE SIMATIC PCS 7 MAINTENANCE STATION RUNTIME BASIC PACKAGE V10.0 (incl. SNMP-OPC server license and 100 Asset TAGs)	4)
1		6ES7658-7GX78-0YB5	SIMATIC PCS 7 MAINTENANCE STATION ENGINEERING V10.0	
	1	6ES7658-3QX88-2YB5	SOFTWARE SIMATIC PDM COMMUNICATION FOUNDATION FIELDBUS V9.3	5)
Automation system				
1		6ES7654-6CL03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, SYSTEM EXPANSIONS CARD 500 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

- 1) The number of POs can be increased later by means of extra volume licenses.
- 2) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).
- 3) The number of PDM TAGs can be increased by means of cumulative TAG licenses.
- 4) The number of Asset TAGs can be increased by means of cumulative Asset TAG licenses.
- 5) Optional for FOUNDATION Fieldbus communication
- 6) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

Sample calculation with asset management single station

The following is a sample calculation with asset management tags, process objects and PDM tags for a given single-user configuration.

The single-user configuration consists of the following:

- an ES/OS/MS single-user
- 200 PROFIBUS PA sensors and actuators
- 100 HART analog sensors and actuators
- 32 FOUNDATION Fieldbus H1 sensors and actuators
- 8 ET 200M IO racks, total of 50 IO modules
- 80 PROFIBUS DP Slaves with EDDL Configuration
- 25 PROFIBUS DP Slaves without EDDL configuration
- 1 AS 410-5H
- 5 PROFIBUS DP and PA networking segments
- 120 process devices with asset monitoring functionality

The components below are needed for the configuration mentioned above:

Item	Counter value	Asset Management TAGs	Process Objects	PDM TAGs
Computer	1	1	0	0
PROFIBUS PA	200	200	0	200
HART	100	100	0	100
FOUNDATION Fieldbus H1	32	32	0	32
ET 200M IM bus interface	8	8	0	0
ET 200M modules	50	0	0	0
PROFIBUS DP slaves - EDDL	80	80	0	80
PROFIBUS DP slaves - without EDDL	25	25	0	0
Automation system	1	1	0	0
Network devices (e.g. switches)	7	7	0	0
Process devices	120	120	120	120
Total				
		574	120	532

Parts list


Required	Optional	Article Number	Product Description	Note
Engineering Station, PDM and Operator Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
1		6ES7651-5AA78-0YA0	SIMATIC PCS 7, SOFTWARE, ES SINGLE STATION V10.0 (AS/OS: PO 250)	1)
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
1		6ES7658-3LD88-0YA5	SOFTWARE SIMATIC PDM PCS 7 V9.3 (100 TAGs)	3)
4		6ES7658-3XC00-2YB5	SIMATIC PDM 10 TAGs	3)
4		6ES7658-3XD00-2YB5	SIMATIC PDM 100 TAGs	3)
1		6ES7658-3QX88-2YB5	SOFTWARE SIMATIC PDM COMMUNICATION FOUNDATION FIELDBUS V9.3	5)
1		6ES7658-7GB78-0YB0	SOFTWARE SIMATIC PCS 7 MAINTENANCE STATION RUNTIME BASIC PACKAGE V10.0 (incl. SNMP-OPC server license and 100 Asset TAGs)	4)
1		6ES7658-7GX78-0YB5	SIMATIC PCS 7 MAINTENANCE STATION ENGINEERING V10.0	
5		6ES7658-7GB00-2YB0	SIMATIC PCS 7 MAINTENANCE STATION RUNTIME ASSET-TAGS (100 TAGs)	4)
1		6ES7654-6CL03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, SYSTEM EXPANSIONS CARD 500 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

- ¹⁾ The number of POs can be increased later by means of extra volume licenses.
- ²⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).
- ³⁾ The number of PDM TAGs can be increased by means of cumulative TAG licenses in steps of 10/100/1000.
- ⁴⁾ The number of Asset TAGs can be increased by means of cumulative Asset TAG licenses.
- ⁵⁾ Optional for FOUNDATION Fieldbus communication.
- ⁶⁾ Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

12.2. PCS 7 Maintenance Station in a Multi-User System with MS/OS Clients and Combined MS/OS Server

In this configuration, the system has one OS Server and three OS Clients. Additionally, the MS server is configured on the OS Server. Depending on the assignment and access rights, each of the OS Clients can be used as a Maintenance Station (MS client).



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
1		6ES7658-3TD88-0YA5	SOFTWARE SIMATIC PDM PCS 7 SERVER V9.3 (100 TAGs)	3)
	1	6ES7658-3QX88-2YB5	SOFTWARE SIMATIC PDM COMMUNICATION FOUNDATION FIELDBUS V9.3	5)
1		6ES7658-7GX78-0YB5	SIMATIC PCS 7 MAINTENANCE STATION ENGINEERING V10.0	
	1	6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	7)
OS Server, Maintenance Server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	6)

Required	Optional	Article Number	Product Description	Note
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)
1		6ES7658-7GB78-0YB0	SOFTWARE SIMATIC PCS 7 MAINTENANCE STATION RUNTIME BASIC PACKAGE V10.0 (incl. SNMP-OPC server license and 100 Asset TAGs)	4)
OS Client				
3		6ES7661-0*	SIMATIC Process Control System IPC647E	6)
3		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	3	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Automation system				
2		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

1) The number of POs can be increased later by means of extra volume licenses.

2) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

3) The number of PDM TAGs can be increased by means of cumulative TAG licenses.

4) The number of Asset TAGs can be increased by means of cumulative Asset TAG licenses

5) Optional for FOUNDATION Fieldbus communication

6) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

7) Optional for the usage of an MS Client on the ES.

Asset Management Client–Server Sample Invoice

The following is a sample calculation for the number of asset management tags, process objects and PDM tags for a given Client–Server configuration.

The Client–Server configuration includes:

- an ES/OS/MS client computer
- one OS Server
- three OS Clients
- 300 PROFIBUS PA sensors and actuators
- 180 HART analog sensors and actuators
- 80 FOUNDATION Fieldbus H1 sensors and actuators
- 20 ET 200M IO racks, total of 135 IO modules
- 160 PROFIBUS DP Slaves with EDDL Configuration
- 60 PROFIBUS DP slaves without EDDL configuration
- 2 AS 410-5Hs
- 8 PROFIBUS DP and PA networking segments
- 240 process devices with asset monitoring functionality

The following components are needed for the configuration:

Item	Counter value	Asset Management TAGs	Process Objects	PDM TAGs
Computer	5	5	0	0
PROFIBUS PA	300	300	0	300
HART	180	180	0	180
FOUNDATION Fieldbus H1	80	80	0	80
ET 200M IM bus interface	20	20	0	0
ET 200M modules	135	0	0	0
PROFIBUS DP slaves - EDDL	160	160	0	160
PROFIBUS DP slaves - without EDDL	60	60	0	0
Automation system	2	2	0	0
Network devices (e.g. switches)	10	10	0	0
Process devices	240	240	240	240
Total				
		1057	240	960

Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	

Required	Optional	Article Number	Product Description	Note
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
1		6ES7658-3TD88-0YA5	SOFTWARE SIMATIC PDM PCS 7 SERVER V9.3 (100 TAGs)	3)
8		6ES7658-3XD00-2YB5	SIMATIC PDM 100 TAGs	3)
6		6ES7658-3XC00-2YB5	SIMATIC PDM 10 TAGs	3)
1		6ES7658-3QX88-2YB5	SOFTWARE SIMATIC PDM COMMUNICATION FOUNDATION FIELDBUS V9.3	5)
1		6ES7658-7GX78-0YB5	SIMATIC PCS 7 MAINTENANCE STATION ENGINEERING V10.0	
	1	6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	7)
OS Server, Maintenance Server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)
1		6ES7658-7GB78-0YB0	SOFTWARE SIMATIC PCS 7 MAINTENANCE STATION RUNTIME BASIC PACKAGE V10.0 (incl. SNMP-OPC server license and 100 Asset TAGs)	4)
1		6ES7658-7GC00-2YB0	SIMATIC PCS 7 MAINTENANCE STATION RUNTIME ASSET-TAGS (1000 TAGs)	4)
OS Client				
3		6ES7661-0*	SIMATIC Process Control System IPC647E	6)
3		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	3	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Automation system				
2		6ES7654-6CP03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1600 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

1) The number of POs can be increased later by means of extra volume licenses.

2) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

3) The number of PDM TAGs can be increased by means of cumulative TAG licenses in steps of 10/100/1000.

4) The number of Asset TAGs can be increased by means of cumulative Asset TAG licenses.


5) Optional for FOUNDATION Fieldbus communication.

6) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

7) Optional for the usage of an MS Client on the ES.

12.3. PCS 7 Maintenance Station in a Multi-User System with MS/OS Clients and Separate MS Server and Red. OS Server

In this configuration, the system has one redundant OS Server pair and three OS Clients. The ES and the Maintenance Station are configured on a separate PC. The Maintenance Server is also configured on a separate PC.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
1		6ES7658-3TD88-0YA5	SOFTWARE SIMATIC PDM PCS 7 Server V9.3 (100 TAGs)	3)
	1	6ES7658-3QX88-2YB5	SOFTWARE SIMATIC PDM COMMUNICATION FOUNDATION FIELDBUS V9.3	5)
1		6ES7658-7GX78-0YB5	SIMATIC PCS 7 MAINTENANCE STATION ENGINEERING V10.0	
	1	6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	7)
OS Server				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	6)

Required	Optional	Article Number	Product Description	Note
1		6ES7652-3BA78-2YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER REDUNDANCY V10.0 (PO 100)	1)
Maintenance server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)
1		6ES7658-7GB78-0YB0	SOFTWARE SIMATIC PCS 7 MAINTENANCE STATION RUNTIME BASIC PACKAGE V10.0 (incl. SNMP-OPC server license and 100 Asset TAGs)	4)
OS Client				
3		6ES7661-0*	SIMATIC Process Control System IPC647E	6)
3		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	3	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Automation system				
2		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

1) The number of POs can be increased later by means of extra volume licenses.

2) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

3) The number of TAGs can be increased by means of cumulative TAG licenses.

4) Note for Asset Runtime:

The number of asset TAGs can be increased by means of cumulative asset TAG licenses. An increase of the asset TAGs requires an increase of AS and OS RT process objects for the maintenance server.


5) Optional for FOUNDATION Fieldbus communication.

6) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

7) Optional for the usage of an MS Client on the ES.

12.4. PCS 7 Maintenance Station in a Multi-User System with MS/OS Clients and Separate Redundant MS Server Pair and OS Server Pair

In this configuration, the system has one redundant OS Server pair and three OS Clients. The ES and the Maintenance Station are configured on a separate PC. The maintenance server is configured on a redundant basis and as a separate system.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
1		6ES7658-3TD88-0YA5	SOFTWARE SIMATIC PDM PCS 7 SERVER V9.3 (100 TAGs)	3)
	1	6ES7658-3QX88-2YB5	SOFTWARE SIMATIC PDM COMMUNICATION FOUNDATION FIELDBUS V9.3	5)
1		6ES7658-7GX78-0YB5	SIMATIC PCS 7 MAINTENANCE STATION ENGINEERING V10.0	
	1	6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	7)
OS Server				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
1		6ES7652-3BA78-2YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER REDUNDANCY V10.0 (PO 100)	1)
OS Server, Maintenance Server				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	6)
1		6ES7652-3BA78-2YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER REDUNDANCY V10.0 (PO 100)	1)
2		6ES7658-7GB78-0YB0	SOFTWARE SIMATIC PCS 7 MAINTENANCE STATION RUNTIME BASIC PACKAGE V10.0 (incl. SNMP-OPC server license and 100 Asset TAGs)	4)
OS Client				
3		6ES7661-0*	SIMATIC Process Control System IPC647E	6)
3		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	3	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Automation system				
2		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

- 1) The number of POs can be increased later by means of extra volume licenses.
- 2) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).
- 3) The number of PDM TAGs can be increased by means of cumulative TAG licenses.
- 4) Note for Asset Runtime:
 - The number of Asset TAGs can be increased by means of cumulative Asset TAG licenses.
 - An increase of the asset TAGs requires an increase of AS and OS RT process objects for the maintenance server.
- 5) Optional for FOUNDATION Fieldbus communication
- 6) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.
- 7) Optional for the usage of an MS Client on the ES.

Sample calculation for a redundant asset management Client–Server System

The following is a sample calculation for the number of asset management tags, process objects and PDM tags for a specified redundant Client–Server configuration.

The redundant Client–Server configuration includes:

- one ES/OS/MS client PC
- one OS/MS server pair
- one OS Server pair
- three OS Clients
- 300 PROFIBUS PA sensors and actuators
- 180 HART analog sensors and actuators
- 80 FOUNDATION Fieldbus H1 sensors and actuators
- 20 ET 200M IO racks, total of 135 IO modules
- 160 PROFIBUS DP Slaves with EDDL Configuration
- 60 PROFIBUS DP slaves without EDDL configuration
- 2 AS 410-5Hs
- 8 PROFIBUS DP and PA networking segments
- 240 process devices with asset monitoring functionality

The following components are needed for the configuration:

Item	Counter value	Asset Management TAGs	Process Objects	PDM TAGs
Computer	8	8	0	0
PROFIBUS PA	300	300	0	300
HART	180	180	0	180
FOUNDATION Fieldbus H1	80	80	0	80
ET 200M IM bus interface	20	20	0	0
ET 200M modules	135	0	0	0
PROFIBUS DP slaves - EDDL	160	160	0	160
PROFIBUS DP slaves - without EDDL	60	60	0	0
Automation system	2	2	0	0
Network devices (e.g. switches)	10	10	0	0
Process devices	240	240	240	240
Total				
		1060	240	960

Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	2)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	

Required	Optional	Article Number	Product Description	Note
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
1		6ES7658-3TD88-0YA5	SOFTWARE SIMATIC PDM PCS 7 SERVER V9.3 (100 TAGs)	
8		6ES7658-3XD00-2YB5	SIMATIC PDM 100 TAGs	
6		6ES7658-3XC00-2YB5	SIMATIC PDM 10 TAGs	
1		6ES7658-3QX88-2YB5	SOFTWARE SIMATIC PDM COMMUNICATION FOUNDATION FIELDBUS V9.3	
1		6ES7658-7GX78-0YB5	SIMATIC PCS 7 MAINTENANCE STATION ENGINEERING V10.0	
	1	6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	3)
OS Server				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	2)
1		6ES7652-3BA78-2YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER REDUNDANCY V10.0 (PO 100)	
OS Server, Maintenance Server				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	2)
1		6ES7652-3BA78-2YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER REDUNDANCY V10.0 (PO 100)	
2		6ES7658-7GB78-0YB0	SOFTWARE SIMATIC PCS 7 MAINTENANCE STATION RUNTIME BASIC PACKAGE V10.0 (incl. SNMP-OPC server license and 100 Asset TAGs)	
2		6ES7658-7GC00-2YB0	SIMATIC PCS 7 MAINTENANCE STATION RUNTIME ASSET-TAGS (1000 TAGs)	
OS Client				
3		6ES7661-0*	SIMATIC Process Control System IPC647E	2)
3		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	3	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Automation system				
2		6ES7654-6CP03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 500 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	1)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

1) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).


2) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

3) Optional for the usage of an MS Client on the ES.

12.5. Asset Management in Flat Hierarchies

From PCS 7 V9.0 onwards, a Maintenance Station can also be used with OS single stations with the following configuration:

- A Redundant OS single station (single station + single station standby)
- Optional: Up to ten non-redundant OS single stations (as reference OS from OS single station)
- MS as a separate PC station



The MS server obtains the data from the ASes via the redundant OS single station.

If the redundant OS single station is deactivated, the data of the ASes are no longer displayed.

NOTE

Messages generated locally on a reference OS are not displayed in the diagnostics screens. For example, self-diagnosis messages are affected by this. The non-accessibility of the reference Oses via the terminal bus is visualized on the MS server.

To display the diagnostic information on the OS single stations, a web server must be configured on the MS server.

The diagnostics screens of the MS server can be accessed from the OS single station via web browser Control.

There are two ways to access the MS server from the OS single station:

- Create a user image on the OS single station in Graphics Designer. Insert a WinCC web browser control into the user image. In process management, you can access the MS via the WinCC web browser control in the user screen.
- Start the WebClient functionality via Internet Explorer/Microsoft Edge Browser.

Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	1) 5)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	1)
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	

Required	Optional	Article Number	Product Description	Note
1		6ES7658-3TD88-0YA5	SOFTWARE SIMATIC PDM PCS 7 SERVER V9.3 (100 TAGs)	1)
	1	6ES7658-3QX88-2YB5	SOFTWARE SIMATIC PDM COMMUNICATION FOUNDATION FIELDBUS V9.3	
1		6ES7658-7GX78-0YB5	SIMATIC PCS 7 MAINTENANCE STATION ENGINEERING V10.0	1)
1		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	1)
Operator Single Station				
1	7	6ES7661-1*	SIMATIC Process Control System IPC847E	5)
1	7	6ES7658-2AA78-0YA0	SIMATIC PCS 7 OS SOFTWARE SINGLE STATION V10.0 INCL. 100 OS RUNTIME PO	1)
1	7	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
		6ES7658-2XA00-0XB0	SIMATIC PCS 7 OS RUNTIME LICENSE (100 TAGS)	
		6ES7658-2EA00-2YB0	SIMATIC PCS 7 OS ARCHIVE (1500 VARIABLES)	
Maintenance Station				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	5)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)
1		6ES7658-7GB78-0YB0	SOFTWARE SIMATIC PCS 7 MAINTENANCE STATION RUNTIME BASIC PACKAGE V10.0 (incl. SNMP-OPC server license and 100 Asset TAGs)	4)
2		6ES7658-7GC00-2YB0	SIMATIC PCS 7 MAINTENANCE STATION RUNTIME ASSET-TAGS (1000 TAGs)	
Automation system				
1		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

1) The number of POs can be increased later by means of extra volume licenses.

2) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

3) The number of PDM TAGs can be increased by means of cumulative TAG licenses.


4) Note for Asset Runtime:

- The number of Asset TAGs can be increased by means of cumulative Asset TAG licenses.
- An increase of the asset TAGs requires an increase of AS and OS RT process objects for the maintenance server.

5) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

12.6. SIMATIC PDM Maintenance Station

This configuration is a single station based on an IPC Microbox 427E.



The PDM MS is based on PCS 7 ES software components.

However, not all the functions of an ES are available (for example, no CFC editor, no HW Configuration for AS systems, etc.).

Instead, the project structure is created in the process device Network view of PDM.

The connection to the process is made to PROFINET networks directly (via internal interface) and to PROFIBUS networks either via S7 CPUs with data record routing or via IE/PB links.

Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station, Operator Station, Maintenance Station				
1		6ES7650-0RJ04-0YX0	SIMATIC PDM Maintenance Station V4.0 based on IPC427E; Core i5-6442EQ; 16 GB DDR4 2400SDRAM, SODIMM; 240 GB solid-state Drive SATA; 3x Gbit Ethernet (IE/PN); no RS232/485, without PCIe; 4 X USB V3.0 (High Current); 24V DC power supply; DIN rail mounting; Windows 10 Enterprise 2019 LTSC, 64Bit, A1 Restore Image pre-installed; Software & licenses are provided via separate delivery of MLFB 6ES7651-5GX04-0YA5	¹⁾
	1	6ES7651-5GX05-0YA5	SIMATIC PDM Maintenance Station Package V5.0, Single License f.1 Installation R-SW, License Key on USB-Stick	

NOTE

¹⁾ The number of PDM TAGs can be increased by means of cumulative TAG licenses. A maximum of 500 PDM tags can be used.

13. SIMATIC Management Console

The SIMATIC Management Console is a software from the SIMATIC PCS 7 product family. The Management Console provides functions for acquiring inventory data and software administration of a PCS 7 system. Software administration using a central Management Console is more efficient than with a local PCS 7 installation.

13.1. Basic Functions of the Management Console

The functions below are available without configuring the Management Console:

- Displaying the computers of a network
In a PCS 7 system, the Management Console can make a connection to the computers on which the "SIMATIC Management Agent" service is installed
- Assigning computers to the Management Console
- Determining groups that contain computers that have to be managed
- Displaying and exporting messages
- Displaying and exporting the event log

13.2. Functions of the Management Console

Using the Management Console, the following functions are available:

- Functions for software administration
- Functions for determining inventory data

13.2.1. Functions for Software Administration

The Management Console offers the following functions for central administration of software on assigned computers:

- On the Management Console, it is possible to determine the SIMATIC software that is installed on a computer.
- To install SIMATIC software packages, the Management Console accesses the functions of the respective product setup routine.
The following installation variants are possible:
 - Installing new software packages
 - Updating software packages
 - Updating the PCS 7 computer
- Using the Management Console, you can specify common installation steps for a group of computers.

NOTE

For this, see the entry "Which products can you install using the SIMATIC Management Console?":
<https://support.industry.siemens.com/cs/ww/en/view/107796665>

13.2.2. Functions for Determining Inventory Data

The Management Console provides functions for determining the inventory data of the objects in a PCS 7 system.

Objects


The source of the inventory data can be objects of the system (online data) or objects in project data (offline data). It is possible to determine inventory data for the following objects of the PCS 7 system:

- PC
- Network components (Ethernet switches)
- Automation systems
- Remote I/Os (including the I/O modules)
- Field devices

Inventory data

Inventory data can include the following information:

- System identification (depending on the identification system; e.g., AKZ/TAG)
- Geographical position (depending on the identification system; e.g., OKZ)
- Description (user-defined)
- Message (user-defined)
- Device name
- Device type
- Serial number
- Article number
- Hardware version
- Firmware version
- Operating system version
- Installed SIMATIC software
- License information (license keys with SIMATIC software)
- Software installed with PCS 7 DVD



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering Station, Operator Station and Automation System				
	1		Existing Engineering Station	1)
1			Separate WIN SERVER 2019	1)
1		6ES7658-5BX78-2YB5	SIMATIC MANAGEMENT CONSOLE V10.0	

NOTE

1) Only ever install one Management Console on one network. Using several Management Consoles can result in inconsistencies.
If possible, install the Management Console on a computer that is not needed for operator control and monitoring.

The Management Console must **not** be installed on one of the following computers:

- A computer with server functions (e.g. a server or single station for OS, BATCH, Route Control, or a Domain Controller)

A computer for acquiring archive data (e.g. Process Historian)

14. Network Architecture


14.1. Overview

Star, line, and tree structures


The rugged SCALANCE network components, active, and managed switches can be used to build cost-effective network topologies for a large number of stations.

SCALANCE offers a wide range of network components to create star, line, and tree structures with a large number of ports.


If multiple switches are needed to realize a high number of ports or to allow the spatial distribution of the switches, then we suggest that you connect the switches as a Fault-Tolerant ring to ensure appropriate availability.



Star




Line



Tree

Fault-tolerant ring

A unique redundancy manager concept enables the administration of several SCALANCE switches faults in a ring backbone for optical, electrical or mixed media process without interrupting the network communication. This function has the complete range of SCALANCE switches (from SCALANCE X200) which are offered with SIMATIC PCS 7.




Ring

Redundant bus with Fault-tolerant rings

SIMATIC PCS 7 provides redundancy from the OS Client right through to the field connection.

Network communication between OS Clients and OS Servers, as well as between OS Servers and AS, can achieve the highest level of availability.

This is the case if each computer and the automation system (two network interfaces per computer and AS) are connected to two separate (redundant) and fault-tolerant networks in ring structure.



Combined systems and terminal bus

When using a common (combined) plant and terminal bus, pay attention to the article entitled "What are the requirements for operating PCS 7 via common system and terminal buses?":

<https://support.industry.siemens.com/cs/ww/en/view/43273606>

The use of VLAN (Virtual Local Area Network) technology makes it possible to split a physical network into logical networks. The use of VLAN allows the system bus and the terminal bus to operate together on one physical network.

NOTE

For more information on configuring a combined system and terminal bus, see the FAQ "How to configure a Virtual Local Area Network (VLAN) in PCS 7?":

<https://support.industry.siemens.com/cs/ww/en/view/66807297>

Backbone networks with 1 to 10 Gbits of bandwidth

For applications where large amounts of data have to be transmitted over the backbone network, the minimum bandwidth of 100 Mbps may no longer be sufficient.

For this purpose, Siemens offers SCALANCE switches with a bandwidth of 1 to 10 Gbit. The high-performance switches deliver the functionality of redundancy management, which makes it possible to set up fault-tolerant ring topologies with single or double redundancy.

14.2. Ring Architectures


14.2.1. High-Speed Ring Error Tolerance

Fault-Tolerant rings based on the High Speed Redundancy Protocol (HRP) are used to form multiple communication paths between switches. If one of the paths fails, a backup path is activated and communication is ensured.

Unlike "spanning-tree" technology, which provides similar functionality, SCALANCE switches reconfigure the existing communication paths fast enough to avoid connected systems (controllers, servers, clients) suffering a loss of communication.

High-speed ring monitoring and reconfiguration is achieved by a SCALANCE switch assuming the role of redundancy manager.

Ring connections between switches can be made via electrical or optical cable connections.




The redundancy manager acts as a switch that opens the Ethernet ring at a predetermined position and controls the cable status. If an error occurs in the cable, the redundancy manager recognizes this, closes the switch, and re-establishes communication.

14.2.2. Ring Connectivity, Standby Redundancy

To connect two separate fault-tolerant Ethernet rings on a redundant basis, there is a second high-speed redundancy function. Although it is necessary to have two connections between the rings for redundancy, only one connection can be active in each case.

To achieve this, one of the two rings to be coupled is equipped with two switches that support the so-called standby redundancy. In this concept, two parallel point-to-point connections monitor each other to ensure that the stand-by connection is activated when the active link fails.

This is achieved by configuring a SCALANCE switch as the standby master and a second SCALANCE switch as the standby slave.



The standby master and standby slave are logically linked. The standby master activates its link and the standby slave deactivates its own link.

Both switches monitor each other's status and the standby slave becomes active if the active connection fails.

The fast activation of the standby slave does not cause a breakdown of the communication between the connected systems (controller, server, clients).

14.2.3. MRP


The Media Redundancy Protocol (MRP) is defined in the IEC 62439 standard and allows ring topologies with up to 50 stations. All stations must support the media redundancy with MRP.

In functional condition, the redundancy manager (a predefined station of the ring) opens the ring and therefore ensures loop-free communication. If the transmission path in the ring is interrupted at one point, e. g. by disconnecting the ring line or failure of a station, the redundancy manager immediately closes the ring and, as a result, provides an alternative communication path. The maximum reconfiguration time is 200 ms.

14.2.4. MRP Interconnection

The MRP Interconnection method is an extension of MRP that enables the redundant coupling of two or more MRP rings in networks without real-time capability.

MRP Interconnection is – as is MRP – specified in the standard IEC 62439-2. A very fast reconfiguration is possible with MRP Interconnection; the reconfiguration time is typically less than 200 milliseconds.



14.3. Redundancy Concepts – Terminal Bus

14.3.1. Introduction

OS Servers/clients as well as Engineering Systems, BATCH servers/clients, Route Control servers/clients and central archive servers can be equipped with a redundant terminal bus connection.

In principle, the structure of this redundant, high-availability terminal bus uses the SIMATIC NET SOFTNET-IE RNA software. This software is based on the Parallel Redundancy Protocol (PRP) as per IEC 62439-3.


SIMATIC NET IE RNA

At each PC station, two of the physically present network adapters are also combined into one logical network adapter.

Only the logical network adapter that has one IP and MAC address is visible to the operating system and the network. Both network cards operate internally using the Parallel Redundancy Protocol (PRP).

The data packets are transmitted in-parallel via both network adapters. On receiver side the first arriving telegram is processed. The telegram sent in parallel is discarded.


Due to the parallel data transmission, a redundant bus must be used without connection between the fault-tolerant Ethernet rings, see Section [14.1](#). Due to the parallel transmission, if an error occurs there is a 0 ms switchover time.



14.3.2. Redundant Terminal Bus

SIMATIC NET SOFTNET IE-RNA redundant network

- Redundant terminal bus connection in every server and client
- Redundant bus with fault-tolerant Ethernet rings
-



Parts list

Required	Optional	Article Number	Product Description	Note
Operator System server				
1		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	1) 2)
Operator System client				
1		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	1) 2)

NOTE SCALANCE switch and network components must be added.
Please note the descriptions of the network topology in this section to select the appropriate configuration and components.

1) The onboard interfaces can be used

2) Single license for one installation

14.4. Redundancy Concepts – System Bus

14.4.1. Introduction

Besides the fault-tolerant ring and redundant bus concepts described above, PCS 7 also provides flexible redundancy solutions for communication via the system bus between OS and AS (controllers).

For redundant communication, SIMATIC S7-400H controllers (as standard or H System), SCALANCE network components, the communication processor CP1623/1628 or corresponding standard network cards (BCE) with the software "HARDNET-IE S7-REDCONNECT" or "SOFTNET-IE S7 REDCONNECT VM" are required for the computers involved.

14.4.2. Standard Automation System

The AS 410 standard automation systems consist of an S7-410-5H controller. The connection to the system bus can either be established via the CP 443-1 communication module or, for S7-410-5H controllers with firmware (FW) V8.1 or higher, via the PROFINET-IO interfaces integrated into the CPU. The following must be considered:

- When using a PROFINET-IO interface for the system bus, it must not be used for PROFINET.
- For system-related reasons, the two PROFINET-IO interfaces must be located in different IP subnets.

You can find additional information at <https://support.industry.siemens.com/cs/ww/en/view/109826184>

NOTE

The file for upgrading the CPU 410-5H firmware can be found in the download article "Operating System Update: CPU410-5H Process Automation":
<https://support.industry.siemens.com/cs/ww/en/view/109476571>


NOTE

An AS410/417 can handle up to 16 OS connection, an AS416 up to 12 OS connections and an AS414 up to 8.

The following is an example of a redundancy configuration:

Single network, single OS Server/single network connection, two communication paths

- one CP1623 in the OS Server, single-user
- two CP443-1 communication processors
- Star network or fault-tolerant ring



Parts list

Required	Optional	Article Number	Product Description	Note
Automation system				
1		6ES7654-6CL04-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 500 PO, AS RT PO 100, 2 X CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	1)
Engineering System and Operator System				
1		6GK1716-0HB18-0ACO	SIMATIC NET, S7-REDCONNECT POWERPACK V18	2)

NOTE

SCALANCE switch and network components must be added. Please note the descriptions of the network topology in this section to select the appropriate configuration and components.

1) REDCONNECT POWERPACKs and CP1623 are needed for each Operator System and Engineering System in which a CP1623 is installed.

2) The parts list is based on the assumption that the selected Operator System and Engineering System hardware is equipped with a CP1623 (industrial Ethernet version of the hardware). Only additional CP1623 communication processors are listed.

14.4.3. High-Availability Automation System AS 410


High-availability AS 410 automation systems consist of two S7-410-5H controllers. For communication, you can use the PROFINET-IO interfaces with firmware V8.1 and up, or equip the 410-5H controllers with two redundant CP443-1 or four redundant CP443-1 communication processors. With regard to the PROFINET-IO interfaces, the following must be observed:

- When using a PROFINET-IO interface for the system bus, it must not be used for PROFINET.
- For system-related reasons, the two PROFINET-IO interfaces must be located in different IP subnets.

Additional information can be found at <https://support.industry.siemens.com/cs/ww/en/view/109826184>

Various redundancy configurations are listed below as examples:

- Concept 1, single network, single OS Server/single-user network connection, two communication paths
 - one CP1623 in the OS Server, single-user
 - two CP443-1 communication processors
 - Star network or fault-tolerant ring
- Concept 2, redundant network, redundant OS Server/single-station network connection, four communication channels
 - two CP1623 in the OS Server, single-user
 - four CP443-1 communication processors
 - redundant fault-tolerant rings



Parts list for concept 1

Required	Optional	Article Number	Product Description	Note
Automation system				
1		6ES7656-6CL33-1CF0	SIMATIC PCS 7 REDUNDANCY AS, 2X CPU 410-5H, 2 DP-MODULE, 2X PROFINET-IO, 2 X CP443-1IE, SYSTEM EXPANSION CARD 500 PO, AS RT PO 100, 2 X 2 10M SYNC-MODULE AND 2 X 1M FO, 1 X UR2-H ALU RACK, 2 X UC 120/230V 10A RED. POWER SUPPLY	³⁾
Engineering System and Operator System				
1		6GK1716-0HB18-0ACO	SIMATIC NET, S7-REDCONNECT POWERPACK V18	¹⁾

Parts list for concept 2

Required	Optional	Article Number	Product Description	Note
Automation system				
1		6ES7656-6CL34-1CF0	SIMATIC PCS 7 REDUNDANCY AS, 2X CPU 410-5H, 2 DP-MODULE, 2X PROFINET-IO, 2x2 CP443-1IE, SYSTEM EXPANSION CARD 500 PO, AS RT PO 100, 2 X 2 10M SYNC-MODULE AND 2 X 1M FO, 1 X UR2-H ALU RACK, 2 X UC 120/230V 10A RED. POWER SUPPLY	¹⁾ ²⁾
Engineering System and Operator System				
1		6GK1716-0HB18-0ACO	SIMATIC NET, S7-REDCONNECT POWERPACK V18	³⁾
1		6GK1162-3AA00	SIMATIC NET COMMUNICATION PROCESSOR CP1623 PCI EXPRESS	³⁾ ⁴⁾

NOTE

SCALANCE switch and network components must be added. Please note the descriptions of the network topology in this section to select the appropriate configuration and components.

¹⁾ Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410 are available (e.g., 24V DC or 110/230V AC).

²⁾ With a configuration as per concept 4 (redundant network, four communication paths) the connection of the CP443-1 to the system bus must be made crosswise ("ABBA") to enable the configuration of the four connection paths in NetPro.


³⁾ REDCONNECT POWERPACKs and CP1623 are needed for each Operator System and Engineering System that is integrated in the system bus.

⁴⁾ The parts list is based on the assumption that the selected Operator System and Engineering System hardware is equipped with a CP1623 (industrial Ethernet version of the hardware); only additional CP1623 communication processors are listed.

14.5. Sample Configurations

This section shows configurations for system and terminal buses based on the redundancy concepts presented in Section 14.3 and Section 14.4. The focus is on the components required for the network infrastructure, which are listed in the parts lists.

14.5.1. Fault-tolerant Ring Architectures with Glass Fiber




Parts list

Required	Optional	Article Number	Product Description	Note
Terminal bus				
2		6GK5206-2BB00-2AC2	SCALANCE XC206-2 MANAGEABLE LAYER 2 IE-SWITCH; 6X 10/100 MBIT/S RJ45 PORTS; 2X 100 MBIT/S ST/BFOC-PORTS	1)
2		6XV1820-5BN10	SIMATIC NET, FIBER OPTIC CABLE, 4 BFOC CONNECTORS, 10M	
5		6XV1870-3QH60	SIMATIC NET INDUSTRIAL ETHERNET TP CORD CABLE RJ45/RJ45, 6M	
		24V DC power supply	Redundant power supply	Section 16.2

Required	Optional	Article Number	Product Description	Note
System bus				
2		6GK5206-2BB00-2AC2	SCALANCE XC206-2 MANAGEABLE LAYER 2 IE-SWITCH; 6X 10/100 MBIT/S RJ45 PORTS; 2X 100 MBIT/S ST/BFOC-PORTS	¹⁾
2		6XV1820-5BN10	SIMATIC NET, FIBER OPTIC CABLE, 4 BFOC CONNECTORS, 10M	
6		6XV1870-3QH60	SIMATIC NET INDUSTRIAL ETHERNET TP CORD CABLE RJ45/RJ45, 6M	
		24V DC power supply	Redundant power supply	Section <u>16.2</u>

NOTE¹⁾ SCALANCE Switch needs a 24V DC power supply.

14.5.2. Electrical fault-tolerant Ring Architectures




Parts list

Required	Optional	Article Number	Product Description	Note
Terminal bus				
2		6GK5208-0BA00-2AC2	SCALANCE XC208 MANAGEABLE LAYER 2 IE-SWITCH; 8X 10/100 MBIT/S RJ45 PORTS	1)
7		6XV1870-3QH60	SIMATIC NET INDUSTRIAL ETHERNET TP CORD CABLE RJ45/RJ45, 6M	
		24V DC power supply	Redundant power supply	Section 16.2
System bus				
2		6GK5208-0BA00-2AC2	SCALANCE XC208 MANAGEABLE LAYER 2 IE-SWITCH; 8X 10/100 MBIT/S RJ45 PORTS	1)
8		6XV1870-3QH60	SIMATIC NET INDUSTRIAL ETHERNET TP CORD CABLE RJ45/RJ45, 6M	
		24V DC power supply	Redundant power supply	Section 16.2

NOTE 1) SCALANCE Switch needs a 24V DC power supply.

14.5.3. Electrical fault-tolerant Ring Structures with Combined System and Terminal Bus




Parts list

Required	Optional	Article Number	Product Description	Note
Shared system and terminal bus				
2		6GK5216-0BA00-2AC2	SCALANCE XC216 MANAGEABLE LAYER 2 IE-SWITCH; 16X 10/100 MBIT/S RJ45 PORTS	1)
11		6XV1870-3QH60	SIMATIC NET INDUSTRIAL ETHERNET TP CORD CABLE RJ45/RJ45, 6M	
		24V DC power supply	Redundant power supply	Section 16.2

NOTE 1) SCALANCE Switch needs a 24V DC power supply.

In spite of the common network, separate network adapters are required for the terminal and system bus.

14.5.4. Redundant Bus Architectures with fault-tolerant Rings




Parts list

Required	Optional	Article Number	Product Description	Note
Terminal bus				
4		6GK5206-2BB00-2AC2	SCALANCE XC206-2 MANAGEABLE LAYER 2 IE-SWITCH; 6X 10/100 MBIT/S RJ45 PORTS; 2X 100 MBIT/S ST/BFOC-PORTS	1)
4		6XV1820-5BN10	SIMATIC NET, FIBER OPTIC CABLE, 4 BFOC CONNECTORS, 10M	
12		6XV1870-3QH60	SIMATIC NET INDUSTRIAL ETHERNET TP CORD CABLE RJ45/RJ45, 6M	
		24V DC power supply	Redundant power supply	Section 16.2
System bus				
4		6GK5206-2BB00-2AC2	SCALANCE XC206-2 MANAGEABLE LAYER 2 IE-SWITCH; 6X 10/100 MBIT/S RJ45 PORTS; 2X 100 MBIT/S ST/BFOC-PORTS	1)
4		6XV1820-5BN10	SIMATIC NET, FIBER OPTIC CABLE, 4 BFOC CONNECTORS, 10M	
8		6XV1870-3QH60	SIMATIC NET INDUSTRIAL ETHERNET TP CORD CABLE RJ45/RJ45, 6M	
		24V DC power supply	Redundant power supply	Section 16.2

NOTE 1) SCALANCE Switch needs a 24V DC power supply.

14.5.5. Redundant Bus Architectures with fault-tolerant Rings and Combined System and Terminal Bus



Parts list

Required	Optional	Article Number	Product Description	Note
Combined system and terminal bus				
4		6GK5206-2BB00-2AC2	SCALANCE XC206-2 MANAGEABLE LAYER 2 IE-SWITCH; 6X 10/100 MBIT/S RJ45 PORTS; 2X 100 MBIT/S ST/BFOC-PORTS	1)
4		6XV1820-5BN10	SIMATIC NET, FIBER OPTIC CABLE, 4 BFOC CONNECTORS, 10M	
20		6XV1870-3QH60	SIMATIC NET INDUSTRIAL ETHERNET TP CORD CABLE RJ45/RJ45, 6M	
		24V DC power supply	Redundant power supply	Section 16.2

NOTE 1) SCALANCE Switch needs a 24V DC power supply.

In spite of the common network, separate network adapters are required for the terminal and system bus.

15. Process Safety

The "Safety Integrated for Process Automation" concept enables the complete integration of safety technology (Process Safety) into the SIMATIC PCS 7 process control system.

As a general rule, when setting up a PCS 7 system with process safety, the same scalable and flexible architectures are possible as for systems without process safety.

It should be noted that a safety-oriented automation system, also known as a fail-safe automation system (F/FH system), is required for the execution of safety-related user programs.

This prerequisite is already met on the hardware side by the AS 410 modular automation system used in the configurations of this document.

Additionally, the license "SIMATIC S7 F Systems Runtime License" is required for each automation system. This is already included in the AS bundles for safety-related automation systems.

The engineering of the safety-related user program can be carried out either with SIMATIC S7 F systems based on CFC logic or optionally with the additional SIMATIC Safety Matrix software based on a cause & effect matrix.

Parts list

Required	Optional	Article Number	Product Description	Note
Additionally required licenses				
1		6ES7833-1CC00-6YX0	SIMATIC S7 F SYSTEMS RUNTIME LICENSE	1)
Engineering Station and Operator Station				
1		6ES7833-1CC46-0YA5	SOFTWARE SIMATIC S7 F SYSTEMS V6.4	
	1	6ES7833-1SM03-0YA5	SOFTWARE SIMATIC SAFETY MATRIX TOOL V6.3	
	1	6ES7833-1SM63-0YA5	SOFTWARE SIMATIC SAFETY MATRIX VIEWER V6.3	2)

NOTE

1) For the processing of safety-related user programs, a license is required for each AS 410 automation system (independent of whether standard or high-availability AS is used). This is already included in the AS bundles for safety-related automation systems.

2) For operating and monitoring the SIMATIC Safety Matrix, a license is required for each OS Single Station/OS Client.

16. 24V DC Supply Concepts

High availability

A reliable power supply is a basic condition for system operation. With MTBF ratings of up to 1 million hours at full load in continuous operation, SITOP power supplies meet the particularly stringent requirements of processing industries. To further increase availability, the system supports redundant establishment of the power supply as well as buffer operation in the case of a power failure.

Universal application

To allow use all over the world, one and three-phase SITOP power supplies have a wide temperature range of -25 ...+70 °C. In addition, they have a wide range of different international approvals (e.g. ATEX, Class I Div2, IECex, GL, ABS, etc.), which means that you can use them all over the world.

Scalability

The SITOP power supplies with different output powers of up to 1000 W can be individually adapted to the system configuration and system expansion. Depending on the requirements, these can be combined with redundancy, selectivity or DC UPS modules. This allows individual expansion up to complete all-round protection.

SITOP power supply portfolio

SITOP PSU8200 with signaling contact

SITOP PSU8200 is perfect for complex systems and machines. The wide-range input allows connection to any mains supply and can withstand large voltage fluctuations. Power Boost supplies up to 3 times the rated current for short periods. In the event of an overload, you can choose between a constant current with automatic restart or a stored switch-off. And the high efficiency reduces energy consumption.



SITOP PSU8400 with IO-Link interface

The SITOP PSU8400 communication-capable power supply can be conveniently parameterized and monitored remotely via the integrated IO-Link interface. However, parameterization and diagnostics can also be carried out on site directly on the device via the display. With an efficiency of up to 96%, it helps to reduce energy consumption.



SITOP PSU8600 power supply system with PROFINET/Industrial Ethernet interface

The SITOP PSU8600 power supply system offers complete integration into an automation system: via PROFINET or Industrial Ethernet with open communication in OPC UA. The operating data is collected and can provide diagnostic and maintenance information. This makes SITOP PSU8600 ideal as an entry point into the digital enterprise. The high efficiency of the basic units of up to 94% ensures low heat loss and thus enables a very compact design. The up to four outputs, which are monitored for overload, also save space for line protection devices.



NOTE

In the next few sub-sections, we will describe preferred 24V supply concepts. Depending on your requirements, you can combine them with different components (e.g. buffered power supply with selective monitoring).

The SITOP library is available for preferred power supply concepts with blocks and faceplates for direct integration into SIMATIC PCS 7. The PCS 7 user automatically receives information on operating states (e. g. buffer operation), maintenance requirements (e.g., replacing batteries) and faults (e.g., short circuits or overloads in 24V circuits).

SITOP library for SIMATIC PCS 7: <https://support.industry.siemens.com/cs/ww/en/view/109476154>

16.1. Basic Power Supplies

Single- and three-phase SITOP modular units are the technology power supplies for demanding solutions. The wide-range input makes it possible to connect to almost any electrical power system worldwide and ensures a high degree of safety even when large voltage fluctuations occur.

They offer outstanding overload characteristics: Power boost delivers up to three-times the rated current for short periods of time, and with extra power of 150%, loads with high power consumption can be connected without any problems.


The very high efficiency keeps energy consumption and heat dissipation in the control cabinet very low and the compact metal housing also saves space.

Single-phase power supplies of S7-300 design can be mounted directly onto S7 rails. The range switchover to 1-phase 120/230V AC grids takes place automatically.



Parts list

Article Number	Product Description
INPUT: 120/230V AC, OUTPUT: DC 24V/5A	
6ES7307-1EA01-0AA0	SIMATIC S7-300 PS307 STABILIZED POWER SUPPLY
6EP3333-8SB00-0AY0	SITOP PSU8200 24V/5A STABILIZED POWER SUPPLY
INPUT: 120/230V AC, OUTPUT: DC 24V/10A	
6ES7307-1KA02-0AA0	SIMATIC S7-300 PS307 STABILIZED POWER SUPPLY
6EP3334-8SB00-0AY0	SITOP PSU8200 24V/10A STABILIZED POWER SUPPLY
INPUT: AC 120–230V DC 110–220V, OUTPUT: DC 24V/20A	
6EP1336-3BA10	SITOP PSU8200 20A STABILIZED POWER SUPPLY
INPUT: AC 120–230V, OUTPUT: DC 24V/40A	
6EP3337-8SB00-0AY0	SITOP PSU8200 40A STABILIZED POWER SUPPLY
INPUT: 3 AC 400–500V OUTPUT: DC 24V/20A	
6EP3436-8SB00-0AY0	SITOP PSU8200 24V/20A STABILIZED POWER SUPPLY
INPUT: 3 AC 400–500V OUTPUT: DC 24V/40A	
6EP1437-3BA10	SITOP PSU8200 24V/40A STABILIZED POWER SUPPLY




Parts list

Article Number	Product Description
INPUT: 3 AC 400–500V OUTPUT: DC 24V/40A	
6EP3437-8SB00-4AY0	SITOP PSU8400 3AC 40A IOL STABILIZED POWER SUPPLY with IO-LINK INTERFACE

16.3. Redundant Power Supply System

For the redundant design of the power supply system PSU8600, the basic units with one output and the redundancy module PSE202U can be used.

They are integrated into the control system via PROFINET. Comprehensive operating and diagnostic information is available such as the voltage and current values of the outputs.




Parts list

Article Number	Product Description	Quantity
INPUT: 3 AC 400–500V OUTPUT: DC 24V/20A		
6EP3436-8SB00-2AY0	SITOP PSU8600, 3 AC, 20A PN regulated power supply	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	1
INPUT: 3 AC 400–500V OUTPUT: DC 24V/40A		
6EP3437-8SB00-2AY0	SITOP PSU8600, 3 AC, 24V/40A Regulated Power Supply	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	2

16.4. Redundant Power Supply with Selective Monitoring of the 24V Feeders


SITOP selectivity modules are an optimum enhancement for all 24V power supplies to distribute the load current to several feeders and to monitor it. Overloads and short-circuits in one or more feeders are detected reliably.

This is ensured even on high-resistance lines and in the case of "creeping" short-circuits. The intact feeders continue to supply the SITOP selectivity modules with 24 V on an absolutely interruption- and reaction-free basis. Their signal contact can be looped across several selectivity modules and can be evaluated as a common alarm in SIMATIC PCS 7.



Parts list

Article Number	Product Description	Quantity
INPUT: 120/230V AC, OUTPUT: DC 24V/10A		
6EP3334-8SB00-0AY0	SITOP PSU8200 24V/10A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	1
6EP1961-2BA11	SITOP PSE200U 3A SELECTIVITY MODULE 4-CHANNEL OUTPUT CURRENT CAN BE SET TO 0.5-3 PER CHANNEL	1 ¹⁾
INPUT: AC 120–230V DC 110–220V, OUTPUT: DC 24V/20A		
6EP1336-3BA10	SITOP PSU8200 20A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	1
6EP1961-2BA21	SITOP PSE200U 10A SELECTIVITY MODULE 4-CHANNEL OUTPUT CURRENT CAN BE SET TO 3-10 PER CHANNEL	1 ¹⁾
INPUT: AC 120–230V, OUTPUT: DC 24V/40A		
6EP3337-8SB00-0AY0	SITOP PSU8200 40A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	2
6EP1961-2BA21	SITOP PSE200U 10A SELECTIVITY MODULE 4-CHANNEL OUTPUT CURRENT CAN BE SET TO 3-10 PER CHANNEL	1 ¹⁾
INPUT: 3 AC 400–500V OUTPUT: DC 24V/20A		
6EP3436-8SB00-0AY0	SITOP PSU8200 24V/20A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	1
6EP1961-2BA21	SITOP PSE200U 10A SELECTIVITY MODULE 4-CHANNEL OUTPUT CURRENT CAN BE SET TO 3-10 PER CHANNEL	1 ¹⁾
INPUT: 3 AC 400–500V OUTPUT: DC 24V/40A		
6EP1437-3BA10	SITOP PSU8200 24V 40A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE OUTPUT CURRENT CAN BE SET TO 3-10 PER CHANNEL	2
6EP1961-2BA21	SITOP PSE200U 10A SELECTIVITY MODULE 4-CHANNEL OUTPUT CURRENT CAN BE SET TO 3-10 PER CHANNEL	1 ¹⁾



Parts list

Article Number	Product Description	Quantity
INPUT: 3 AC 400–500V OUTPUT: DC 24V/40A		
6EP3437-8SB00-4AY0	SITOP PSU8400 3AC 40A IOL STABILIZED POWER SUPPLY with IO-LINK INTERFACE	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE OUTPUT CURRENT CAN BE SET TO 3-10 PER CHANNEL	2
6EP1961-2BA21	SITOP PSE200U 10A SELECTIVITY MODULE 4-CHANNEL OUTPUT CURRENT CAN BE SET TO 3-10 PER CHANNEL	1 ¹⁾

NOTE ¹⁾ Depending on the requirements, the output current of the power supply unit can be distributed to several PSE200Us (signal contact can be looped across several PSE200Us).

The redundant power supply with selective monitoring of the 24V feeders is particularly suitable for supplying power to the 24V consumers at the field level.

The following modules can also be used as alternatives to the SITOP PSE200U selectivity module:


Article Number	Product Description	Quantity
6EP4437-7FB00-3CX0	SITOP SEL1200 10A SELECTIVITY MODULE 4-CHANNEL OUTPUT CURRENT CAN BE SET TO 2-10 A PER CHANNEL	1
6EP4438-7FB00-3DX0	SITOP SEL1200 10A SELECTIVITY MODULE 8-CHANNEL OUTPUT CURRENT CAN BE SET TO 2-10 A PER CHANNEL	1
6EP4437-7EB00-3CX0	SITOP SEL1400 10A SELECTIVITY MODULE 4-CHANNEL OUTPUT CURRENT CAN BE SET TO 2-10 A PER CHANNEL A	1
6EP4438-7EB00-3DX0	SITOP SEL1400 10A SELECTIVITY MODULE 8-CHANNEL OUTPUT CURRENT CAN BE SET TO 2-10 A PER CHANNEL	1

16.5. Device Combination of Power Supply and SITOP Selectivity System SEL1600 IOL

SITOP selectivity modules are an optimum enhancement for all 24V power supplies to distribute the load current to several feeders and to monitor it. Overloads and short-circuits in one or more feeders are detected reliably. The SITOP SEL1600 selectivity module offers many options for a wide variety of applications, handlings and areas of application. Whether with or without IO-Link.


The basic module offers four outputs for the safe shutdown of faulty 24 V load feeders and the non-reactive supply of other 24 V load feeders. The integrated IO-Link interface enables bidirectional communication for remote parameterization and remote diagnosis of operating status and operating values as well as for targeted switching on/off of outputs.

The basic module with integrated display can be combined with up to nine SEL1600 expansion modules to expand the four monitored outputs to up to 40 outputs. The modules are lined up without any lateral installation distance and simply connected by means of a 24 V connection bracket and ribbon cable. The pluggable output terminals facilitate wiring and commissioning. Like the basic module, the expansion module has four outputs for the safe shutdown of faulty 24 V consumer feeders and the non-reactive supply of further 24 V consumer feeders.



Parts list

Article Number	Product Description	Quantity
INPUT: AC 120–230V, OUTPUT: DC 24V/40A		
6EP3337-8SB00-0AY0	SITOP PSU8200 40A STABILIZED POWER SUPPLY	1
6EP4437-8FB00-4CY0	SITOP SEL1600 IOL SELECTIVITY MODULE EXPANDABLE TO UP TO 40 OUTPUTS OUTPUT CURRENT CAN BE SET TO 0-10 A PER CHANNEL	1
6EP4437-8FB00-0CY0	SITOP SEL1600 EXPANSION MODULE 4-CHANNEL OUTPUT CURRENT CAN BE SET TO 0-10 A PER CHANNEL	2
INPUT: 3 AC 400–500V OUTPUT: DC 24V/40A		
6EP1437-3BA10	SITOP PSU8200 24V 40A STABILIZED POWER SUPPLY	1
6EP4437-8FB00-4CY0	SITOP SEL1600 IOL SELECTIVITY MODULE EXPANDABLE TO UP TO 40 OUTPUTS OUTPUT CURRENT CAN BE SET TO 0-10 A PER CHANNEL	1
6EP4437-8FB00-0CY0	SITOP SEL1600 EXPANSION MODULE 4-CHANNEL OUTPUT CURRENT CAN BE SET TO 0-10 A PER CHANNEL	2




Parts list

Article Number	Product Description	Quantity
INPUT: 3 AC 400–500V OUTPUT: DC 24V/40A		
6EP3437-8SB00-4AY0	SITOP PSU8400 3AC 40A IOL STABILIZED POWER SUPPLY with IO-LINK INTERFACE	1
6EP4437-8FB00-4CY0	SITOP SEL1600 IOL SELECTIVITY MODULE EXPANDABLE TO UP TO 40 OUTPUTS OUTPUT CURRENT CAN BE SET TO 0-10 A PER CHANNEL	1
6EP4437-8FB00-0CY0	SITOP SEL1600 EXPANSION MODULE 4-CHANNEL OUTPUT CURRENT CAN BE SET TO 0-10 A PER CHANNEL	2

16.6. Buffered Power Supply


A power failure not only interrupts the AC power supply but also the 24V supply and the automation system that is connected to it. Costly downtime and undefined system states can be the result.

The SITOP UPS1600 DC UPS with battery modules prevents this scenario by providing reliable backup of the 24V supply for up to several hours. Depending on the version of the DC UPS, it is integrated into the control system by means of digital inputs/outputs or via PROFINET.



Parts list

Article Number	Product Description	Quantity
INPUT: 120/230V AC, OUTPUT: DC 24V/10A		
6EP3334-8SB00-0AY0	SITOP PSU8200 24V/10A STABILIZED POWER SUPPLY	1
6EP4134-3AB00-2AY0	SITOP UPS1600 10A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET INTERFACE	1
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	1-6 ²⁾
INPUT: AC 120–230V DC 110–220V, OUTPUT: DC 24V/20A		
6EP1336-3BA10	SITOP PSU8200 20A STABILIZED POWER SUPPLY	1
6EP4136-3AB00-2AY0	SITOP UPS1600 20A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET	1
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	1-6 ²⁾
INPUT: AC 120–230V DC 110–220V, OUTPUT: DC 24V/40A		
6EP3337-8SB00-0AY0	SITOP PSU8200 40A STABILIZED POWER SUPPLY	1
6EP4136-3AB00-2AY0	SITOP UPS1600 20A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET	1
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	1-6 ²⁾
INPUT: 3 AC 400-500V OUTPUT: DC 24V/20A		
6EP3436-8SB00-0AY0	SITOP PSU8200 24V/20A STABILIZED POWER SUPPLY	1
6EP4136-3AB00-2AY0	SITOP UPS1600 20A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET	1
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	1-6 ²⁾
INPUT: 3 AC 400-500V OUTPUT: DC 24V/40A		
6EP1437-3BA10	SITOP PSU8200 24V 40A STABILIZED POWER SUPPLY	1
6EP4137-3AB000-2AY0	SITOP UPS1600 40A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET	1
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	1-6 ²⁾



Parts list

Article Number	Product Description	Quantity
INPUT: 3 AC 400-500V OUTPUT: DC 24V/40A		
6EP3437-8SB00-4AY0	SITOP PSU8400 3AC 40A IOL STABILIZED POWER SUPPLY with IO-LINK INTERFACE	1
6EP4137-3AB000-2AY0	SITOP UPS1600 40A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET	1
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	1-6 ²⁾


NOTE ²⁾ The backup time is governed by the load current and the number of battery modules, see the table below.

When choosing the correct DC UPS configuration combined with other battery modules (lead, pure lead, LiFePo, and capacitances) the SITOP Selection Tool helps you in an optimum way:
www.siemens.com/selection-tool

Load current	Battery module 12 Ah (6EP4135-0GE00-0AY0)
4 A	2.3 h
6 A	1.4 h
10 A	48.6 min
20 A	19.6 min
40 A	8.5 min (2 x 12 Ah)


16.7. Redundant Power Supply with Buffering

If you have more demanding requirements of a reliable 24V supply, it is possible to combine a redundant power supply with a DC UPS. This ensures that 24V power continues to be supplied even if a power supply fails or there is a power outage.



Parts list

Article Number	Product Description	Quantity
INPUT: 120/230V AC, OUTPUT: DC 24V/10A		
6EP3334-8SB00-0AY0	SITOP PSU8200 24V/10A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	1
6EP4134-3AB00-2AY0	SITOP UPS1600 10A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET INTERFACE	1
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	1-6 ²⁾
INPUT: AC 120-230V DC 110-220V, OUTPUT: DC 24V/20A		
6EP1336-3BA10	SITOP PSU8200 20A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	1
6EP4136-3AB00-2AY0	SITOP UPS1600 20A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET	1
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	1-6 ²⁾
INPUT: AC 120-230V DC 110-220V, OUTPUT: DC 24V/40A		
6EP3337-8SB00-0AY0	SITOP PSU8200 40A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	2
6EP4136-3AB00-2AY0	SITOP UPS1600 20A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET	1
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	1-6 ²⁾
INPUT: 3 AC 400-500V OUTPUT: DC 24V/20A		
6EP3436-8SB00-0AY0	SITOP PSU8200 24V/20A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	1
6EP4136-3AB00-2AY0	SITOP UPS1600 20A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET	1
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	1-6 ²⁾
INPUT: 3 AC 400-500V OUTPUT: DC 24V/40A		
6EP1437-3BA10	SITOP PSU8200 24V 40A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	2
6EP4137-3AB000-2AY0	SITOP UPS1600 40A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET	1
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	1-6 ²⁾



Parts list

Article Number	Product Description	Quantity
INPUT: 3 AC 400-500V OUTPUT: DC 24V/40A		
6EP3437-8SB00-4AY0	SITOP PSU8400 3AC 40A IOL STABILIZED POWER SUPPLY with IO-LINK INTERFACE	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	2
6EP4137-3AB000-2AY0	SITOP UPS1600 40A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET	1
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	1-6 ²⁾

NOTE


²⁾ The backup time is governed by the load current and the number of battery modules, see the table below.

When choosing the correct DC UPS configuration combined with other battery modules (lead, pure lead, LiFePo, and capacitances) the SITOP Selection Tool helps you in an optimum way:
www.siemens.com/selection-tool

Load current	Battery module 12 Ah (6EP4135-0GE00-0AY0)
4 A	2.3 h
6 A	1.4 h
10 A	48.6 min
20 A	19.6 min
40 A	8.5 min (2 x 12 Ah)

16.8. Redundant Power Supply with Redundant Buffering

If the requirements of the 24V power supply are particularly demanding, it is possible to set up the power supplies with DC UPS on a redundant basis. This ensures that 24V power continues to be supplied even if there is a power outage, or a power supply or DC UPS component fails.



Parts list

Article Number	Product Description	Quantity
INPUT: 120/230V AC, OUTPUT: DC 24V/10A		
6EP3334-8SB00-0AY0	SITOP PSU8200 24V/10A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	1
6EP4134-3AB00-2AY0	SITOP UPS1600 10A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET INTERFACE	2
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	2x 1-6 ²⁾
INPUT: AC 120-230V DC 110-220V, OUTPUT: DC 24V/20A		
6EP1336-3BA10	SITOP PSU8200 20A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	1
6EP4136-3AB00-2AY0	SITOP UPS1600 20A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET	2
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	2x 1-6 ²⁾
INPUT: AC 120-230V DC 110-220V, OUTPUT: DC 24V/40A		
6EP3337-8SB00-0AY0	SITOP PSU8200 40A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	2
6EP4137-3AB00-2AY0	SITOP UPS1600 40A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET	2
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	2x 1-6 ²⁾

INPUT: 3 AC 400-500V OUTPUT: DC 24V/20A		
6EP3436-8SB00-0AY0	SITOP PSU8200 24V/20A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	1
6EP4136-3AB00-2AY0	SITOP UPS1600 20A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET	2
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	2x 1-6 ²⁾
INPUT: 3 AC 400-500V OUTPUT: DC 24V/40A		
6EP1437-3BA10	SITOP PSU8200 24V 40A STABILIZED POWER SUPPLY	2
6EP1961-3BA21	SITOP PSE202U REDUNDANCY MODULE INPUT/OUTPUT: DC 24V/40A	2
6EP4137-3AB00-2AY0	SITOP UPS1600 40A UNINTERRUPTIBLE POWER SUPPLY WITH ETHERNET/PROFINET	2
6EP4135-0GE00-0AY0	SITOP BAT1600 BATTERY MODULE WITH MAINTENANCE-FREE SEALED LEAD-ACID BATTERY FOR 24V DC 12 AH SITOP DC UPS MODULES	2x 1-6 ²⁾
Alternative to SITOP PSU8200 24V/10A REGULATED POWER SUPPLY		
6EP3437-8SB00-4AY0	SITOP PSU8400 3AC 40A IOL STABILIZED POWER SUPPLY with IO-LINK INTERFACE	2

NOTE

²⁾ The backup time is governed by the load current and the number of battery modules, see the table below.


When choosing the correct DC UPS configuration combined with other battery modules (lead, pure lead, LiFePo, and capacitances) the SITOP Selection Tool helps you in an optimum way:
www.siemens.com/selection-tool

Load current	Battery module 12 Ah (6EP4135-0GE00-0AY0)
4 A	2.3 h
6 A	1.4 h
10 A	48.6 min
20 A	19.6 min
40 A	8.5 min (2 x 12 Ah)

16.9. Power Supply System with Selective Monitoring and Buffering

The SITOP PSU8600 power supply system consists of a PSU8600 basic unit, up to four CNX8600 expansion modules with 4 or 8 outputs, and a maximum of two BUF8600 or UPS8600 buffer components with BAT8600 batteries connected. Depending on the expansion, up to 36 DC outputs can be selectively monitored and power failures can be bridged for up to several hours.

The modular system makes possible individual combination of the power supply system without any additional wiring. The order of the expansion modules and buffer modules is irrelevant in this case. They are integrated into the control system via PROFINET. Comprehensive operating and diagnostic information is available such as the voltage and current values of the individual outputs.



Parts list**Three-phase**

Article Number	Product Description	Quantity
INPUT: 3 AC 400-500V OUTPUT: DC 24V/20A (4x 5A)		
6EP3436-8MB00-2CY0	SITOP PSU8600 20A PN (4x 5A) Regulated power supply	1
6EP4436-8XB00-0CY0	SITOP CNX8600 (4x 5A) expansion module ³⁾	0-4
6EP4295-8HB00-0XY0	SITOP BUF8600 – buffer capacity: 10 s/40A	0-2
6EP4197-8AB00-0XY0	SITOP UPS8600 UPS module	0-2
6EP4143-8JB00-0XY0	SITOP BAT8600 LiFePO4 battery module, DC 48V/264 Wh	0-5 ⁴⁾
6EP4145-8GB00-0XY0	SITOP BAT8600 Pb battery module, DC 48V/380 Wh	0-5 ⁴⁾
INPUT: 3 AC 400-500V OUTPUT: DC 24V/40A (4x 10A)		
6EP3437-8MB00-2AY0	SITOP PSU8600 40A PN (4x 10A) Regulated power supply	1
6EP4437-8XB00-0CY0	SITOP CNX8600 (4x 10A) expansion module ³⁾	0-4
6EP4295-8HB00-0XY0	SITOP BUF8600 – buffer capacity: 10 s/40A	0-2
6EP4197-8AB00-0XY0	SITOP UPS8600 UPS module	0-2
6EP4143-8JB00-0XY0	SITOP BAT8600 LiFePO4 battery module, DC 48V/264 Wh	0-5 ⁴⁾
6EP4145-8GB00-0XY0	SITOP BAT8600 Pb battery module, DC 48V/380 Wh	0-5 ⁴⁾

Single-phase

Article Number	Product Description	Quantity
INPUT: 1 AC 100-240V OUTPUT: DC 24V/20A (4x 5A)		
6EP3336-8MB00-2CY0	SITOP PSU8600 1 AC 20A PN (4x 5A) regulated power supply	1
6EP4436-8XB00-0CY0	SITOP CNX8600 (4x 5A) expansion module ³⁾	0-4
6EP4295-8HB00-0XY0	SITOP BUF8600 – buffer capacity: 10 s/40A	0-2
6EP4197-8AB00-0XY0	SITOP UPS8600 UPS module	0-2
6EP4143-8JB00-0XY0	SITOP BAT8600 LiFePO4 battery module, DC 48V/264 Wh	0-5 ⁴⁾
6EP4145-8GB00-0XY0	SITOP BAT8600 Pb battery module, DC 48V/380 Wh	0-5 ⁴⁾

NOTE

³⁾ Depending on the requirements, the output current of the power supply unit can be distributed to other (max. 4 more) CNX8600s.

⁴⁾ For each SITOP UPS8600 UPS module used, up to five SITOP BAT8600 of the same type can be used.

Buffer modules

Article Number	Product Description
6EP4297-8HB00-0XY0	SITOP BUF8600 – buffer capacity: 100 ms/40A
6EP4297-8HB10-0XY0	SITOP BUF8600 – buffer capacity: 300 ms/40A
6EP4293-8HB00-0XY0	SITOP BUF8600 – buffer capacity: 4 s/40A
6EP4295-8HB00-0XY0	SITOP BUF8600 – buffer capacity: 10 s/40A

Expansion modules

Article Number	Product Description
6EP4437-8XB00-0CY0	SITOP CNX8600 – Expansion of outputs: 4 x 10 A
6EP4436-8XB00-0CY0	SITOP CNX8600 – Expansion of outputs: 4 x 5 A
6EP4436-8XB00-0DY0	SITOP CNX8600 – Expansion of outputs: 8 x 2.5A

17. Possibilities for Data Exchange

Client–Server system and OpenPCS 7

SIMATIC PCS 7 offers access to all real-time values, archive values, and messages at any time. The OpenPCS 7 software is the extensive interface for this access. It establishes the connection to the SIMATIC PCS 7 OS Servers as well as to the Central Archive servers and offers access to all the data via standard OPC server technology. It combines OPC UA DA (Unified Architecture), OPC DA (Data Access), OPC HDA (Historical Data Access), OPC AE (Alarms & Events) and OPC HAE (Historical Alarms & Events) in one system.

In addition to this, it is also possible to achieve simple, standardized direct access to the archive data in the Microsoft SQL Server database of the Operator System via OLE-DB.

Small system


Smaller systems benefit from a cost-effective combination of functionality from OpenPCS 7 and OS Clients.

Large system

For large high-performance applications, OpenPCS 7 runs on a standalone PC and provides access to all the data that is located on multiple redundant SIMATIC PCS 7 systems composed of an OS Server and a Process Historian.

17.1. Small OS Client/OS Server System and OpenPCS 7

In this configuration, the system has one OS Server and one OS Client. The OpenPCS 7 Station is configured on an OS Client.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering System				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	

Required	Optional	Article Number	Product Description	Note
OS Server				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	4)
1		6ES7658-2BA78-0YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER V10.0 (PO 100)	1)
OS Client				
1		6ES7661-0*	SIMATIC Process Control System IPC647E	4)
1		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
OS Client and OpenPCS 7 station				
1		6ES7661-0*	SIMATIC Process Control System IPC647E	4)
1		A5E02639550	DESKTOP ADAPTER NETWORK CARD	3)
1		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
1		6ES7658-0GX78-2YB0	SOFTWARE SIMATIC PCS 7 OPENPCS 7/OS-CLIENT V10.0	
	1	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	
Automation system				
1		6ES7654-6CN03-3BF0	SIMATIC PCS 7 SINGLE AS, CPU 410-5H, 1X DP-MODULE, 2x PROFINET-IO, SYSTEM EXPANSIONS CARD 1000 PO, AS RT PO 100, CP443-1IE, UR2 ALU RACK, 1 X UC 120/230V 10A POWER SUPPLY	2)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

1) The number of POs can be increased later by means of extra volume licenses.

2) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

3) Necessary for the Enterprise network connection when using a redundant terminal bus.


4) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

Firewall applications between the terminal bus and the perimeter network, and between the perimeter network and the enterprise network are not listed but are necessary.

Network components for the perimeter network and enterprise network connection have not been listed.

17.2. Large OS Client/OS Server System and OpenPCS 7

In this configuration, the system has one redundant OS Server pair and two OS Clients. The Process Historian and the Information Server are configured on separate PCs. The OpenPCS 7 Station is configured on a separate PC.



Parts list

Required	Optional	Article Number	Product Description	Note
Engineering System				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	8)
1		6ES7658-5AX78-0YA5	SOFTWARE SIMATIC PCS 7 AS/OS ENGINEERING V10.0	
1		6GK1162-3AA00	SIMATIC NET COMMUNICATION PROCESSOR CP 1623 PCI EXPRESS	1)
1		6GK1716-0HB18-0AC0	SIMATIC NET, S7-REDCONNECT POWERPACK V18	3)
1		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	8)
	1	6ES7658-1CX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION CROSS MANAGER V10.0	
	1	6ES7658-1FX78-2YA5	SOFTWARE SIMATIC PCS 7 VERSION TRAIL V10.0	
	1	6ES7658-1DX78-2YB5	SOFTWARE SIMATIC PCS 7 IMPORT EXPORT ASSISTANT V10.0	
OS Server				
2		6ES7661-1*	SIMATIC Process Control System IPC847E	8)
1		6ES7652-3BA78-2YA0	SOFTWARE SIMATIC PCS 7 OS-SERVER REDUNDANCY V10.0 (PO 100)	2) 7)
2		6GK1162-3AA00	SIMATIC NET COMMUNICATION PROCESSOR CP 1623 PCI EXPRESS	1)
2		6GK1716-0HB18-0AC0	SIMATIC NET, S7-REDCONNECT POWERPACK V18	3)
1		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	
Process Historian				
1		6ES7661-1*	SIMATIC Process Control System IPC847E	8)
1		A5E02639550	DESKTOP ADAPTER NETWORK CARD	6)
1		6ES7652-7BX78-2YB0	SOFTWARE SIMATIC PCS 7 Process Historian Basic Package V10.0	
1		6XV1870-3RH60	SIMATIC NET INDUSTRIAL ETHERNET TP XP CORD RJ45/RJ45, 6M	
1		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	
Information Server				
1		6ES7661-0*	SIMATIC Process Control System IPC647E	8)
1		6ES7652-7EX78-2YB0	SOFTWARE SIMATIC PCS 7 INFORMATION SERVER BASIC PACKAGE V10.0	
1		6ES7652-7YA00-2YB0	SOFTWARE SIMATIC PCS 7 INFORMATION SERVER CLIENT ACCESS 1 CLIENT	
OS Client				
2		6ES7661-0*	SIMATIC Process Control System IPC647E	8)
2		6ES7658-2CX78-0YB5	SOFTWARE SIMATIC PCS 7 OS-CLIENT V10.0	
2		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	7)
	2	6ES7652-0XD78-2YB5	SOFTWARE SIMATIC PCS 7 SFC VISUALIZATION V10.0	

Required	Optional	Article Number	Product Description	Note
OpenPCS 7 station				
1		6ES7661-0*	SIMATIC Process Control System IPC647E	8)
1		A5E02639550	DESKTOP ADAPTER NETWORK CARD	6)
1		6ES7658-0HX78-2YB0	SOFTWARE SIMATIC PCS 7 OPENPCS 7 V10.0	
1		6GK1711-1EW18-0AA0	SIMATIC NET SOFTNET-IE RNA V18 REDUNDANT NETWORK ACCESS	7)
Automation system				
2		6ES7656-6CP33-1CF0	SIMATIC PCS 7 REDUNDANCY AS, 2X CPU 410-5H, 2 DP-MODULE, 2X PROFINET-IO, SYSTEM EXPANSION CARD 1600, AS RT PO 100, 2 X 2 10M SYNC-MODULE AND 2 X 1M FO, 2 X CP443-1 IE/PN, 1 X UR2-H ALU RACK, 2 X UC 120/230V 10A RED. POWER SUPPLY	4)
		24V DC power supply	Redundant power supply	Section 16.2

NOTE

1) Needed if a redundant system bus is chosen.

2) The number of POs can be increased later by means of extra volume licenses.

3) Necessary if a redundant system bus or a redundant automation system is chosen.

4) Please use the PCS 7 AS configurator, since different versions of the PCS 7 AS 410-5H are available (e.g., 24V DC or 110/230V AC).

5) The tag inventory can be expanded using cumulative volume licenses (SIMATIC PCS 7 OS/PH Archive up to a maximum of 120,000 archive tags).

6) Necessary for the Enterprise network connection when using a redundant terminal bus.

7) The onboard interfaces can be used.

Single License for one installation. Necessary if a redundant terminal bus is selected.

8) Use the IPC Configurator to adapt the IPC hardware components to the requirements of the respective application.

Firewall applications between the terminal bus and the perimeter network, and between the perimeter network and the enterprise network are not listed but are necessary.

Network components for perimeter network and enterprise network connection are not listed.

18. AS-OS PO Counting

18.1. Process Objects

The following applies to the licensing of process objects (POs) in SIMATIC PCS 7:

The following are counted as process objects by PCS 7:

- all SFCs
- all block instances that meet the following criteria:
 - they can be operated and monitored
 - they generate messages
 - they are not diagnostic modules

These objects are transferred to the OS and require a license.

Blocks that can be operated and monitored have the attribute "S7_m_c = true" in their block properties.

Process objects can include the following blocks and objects:

- Blocks for operator control and monitoring of a system
- Objects for automation
- Objects for signal capture and processing

As a general rule, 0.75...1.5 I/Os correspond to one process object.

For PCS 7 licensing, the total number of process objects is counted regardless of the number of inputs and outputs. The data that is exchanged with other automation systems also has no effect on the number of process objects.

NOTE

The described PO count may vary for individual blocks. For example, the Model Predictive Controller (MPC) controller block is counted with 100 POs.

NOTE

Under the following link, you can find an FAQ on how to count POs:

<https://support.industry.siemens.com/cs/ww/en/view/38855207>

More information about licenses and quantity structures can be found in the "PCS 7 Licenses and configuration limits (V10.0)" manual:

<https://support.industry.siemens.com/cs/ww/en/view/109794371>

18.2. Cumulative Licenses

The cumulative licenses below are available for individual SIMATIC software products:

Article Number	Product Description
AS Runtime license	
6ES7653-2BA00-0XB5	SOFTWARE SIMATIC PCS 7 RUNTIME LICENSE AS (PO 100)
6ES7653-2BB00-0XB5	SOFTWARE SIMATIC PCS 7 RUNTIME LICENSE AS (PO 1000)
6ES7653-2BC00-0XB5	SOFTWARE SIMATIC PCS 7 RUNTIME LICENSE AS (PO 10.000)
OS Runtime license	
6ES7658-2XA00-0XB0	SOFTWARE SIMATIC PCS 7 OS RUNTIME LICENSE (PO 100)
6ES7658-2XB00-0XB0	SOFTWARE SIMATIC PCS 7 OS RUNTIME LICENSE (PO 1000)
6ES7658-2XC00-0XB0	SOFTWARE SIMATIC PCS 7 OS RUNTIME LICENSE (PO 5000)
OS archive	
6ES7658-2EA00-2YB0	SIMATIC PCS 7, OS ARCHIVE (1.500 VAR)
6ES7658-2EB00-2YB0	SIMATIC PCS 7, OS ARCHIVE (5.000 VAR)
6ES7658-2EC00-2YB0	SIMATIC PCS 7, OS ARCHIVE (10.000 VAR)
6ES7658-2ED00-2YB0	SIMATIC PCS 7, OS ARCHIVE (30.000 VAR)
PDM	
6ES7658-3XC00-2YB5	SIMATIC PDM (10 TAGs)
6ES7658-3XD00-2YB5	SIMATIC PDM (100 TAGs)
6ES7658-3XE00-2YB5	SIMATIC PDM (1000 TAGs)
BATCH	
6ES7657-0XA00-0YB0	SIMATIC PCS 7, SIMATIC BATCH (1 UNIT)
6ES7657-0XB00-0YB0	SIMATIC PCS 7, SIMATIC BATCH (10 UNITS)
6ES7657-0XC00-0YB0	SIMATIC PCS 7, SIMATIC BATCH (50 UNITS)
Route Control Routes	
6ES7658-7FF00-0XB0	SIMATIC PCS 7, SIMATIC ROUTE CONTROL (10 ROUTES)
6ES7658-7FG00-0XB0	SIMATIC PCS 7, SIMATIC ROUTE CONTROL (50 ROUTES)
Maintenance RT	
6ES7658-7GB00-2YB0	SIMATIC PCS7, MAINTENANCE STATION RUNTIME (100 TAGs)
6ES7658-7GC00-2YB0	SIMATIC PCS7, MAINTENANCE STATION RUNTIME (1000 TAGs)
SIMATIC Management Console	
6ES7658-5BA00-2YB5	SIMATIC PCS 7, MANAGEMENT CONSOLE (10 AGENTS)
6ES7658-5BB00-2YB5	SIMATIC PCS 7, MANAGEMENT CONSOLE (50 AGENTS)
6ES7658-5BC00-2YB5	SIMATIC PCS 7, MANAGEMENT CONSOLE (100 AGENTS)
Information Server - Client Access	
6ES7652-7YA00-2YB0	SIMATIC PCS 7, INFORMATION SERVER (1 CLIENT)
6ES7652-7YB00-2YB0	SIMATIC PCS 7, INFORMATION SERVER (3 CLIENTS)
6ES7652-7YC00-2YB0	SIMATIC PCS 7, INFORMATION SERVER (5 CLIENTS)
6ES7652-7YD00-2YB0	SIMATIC PCS 7, INFORMATION SERVER (10 CLIENTS)
Information Server - Data Source Access	
6ES7652-7YE00-2YB0	SIMATIC PCS 7, INFORMATION SERVER DATASOURCE ACCESS (1 SOURCE)
6ES7652-7YF00-2YB0	SIMATIC PCS 7, INFORMATION SERVER DATASOURCE ACCESS (3 SOURCES)
OS Web server	
6ES7658-2GE00-0XB0	SIMATIC PCS 7, WEB SERVER (1 CLIENT)
6ES7658-2GF00-0XB0	SIMATIC PCS 7, WEB SERVER (5 CLIENTS)
6ES7658-2GG00-0XB0	SIMATIC PCS 7, WEB SERVER (10 CLIENTS)
Information Server - Data Source Access	
6ES7652-7YE00-2YB0	SIMATIC PCS 7, INFORMATION SERVER DATASOURCE ACCESS (1 SOURCE)
6ES7652-7YF00-2YB0	SIMATIC PCS 7, INFORMATION SERVER DATASOURCE ACCESS (3 SOURCES)

19. Service and support

Industry Online Support

Do you have any questions or need assistance?

Siemens Industry Online Support offers round the clock access to our entire service and support know-how and portfolio.

The Industry Online Support is the central address for information about our products, solutions and services.

Product information, manuals, downloads, FAQs, application examples and videos – all information is accessible with just a few mouse clicks:

support.industry.siemens.com

Technical Support

The Technical Support of Siemens Industry provides you fast and competent support regarding all technical queries with numerous tailor-made offers

– ranging from basic support to individual support contracts.

Please send queries to Technical Support via Web form:

siemens.com/SupportRequest

SITRAIN – Digital Industry Academy

We support you with our globally available training courses for industry with practical experience, innovative learning methods and a concept that's tailored to the customer's specific needs.

For more information on our offered trainings and courses, as well as their locations and dates, refer to our web page:

siemens.com/sitrain

Service offer

Our range of services includes the following:

- Plant data services
- Spare parts services
- Repair services
- On-site and maintenance services
- Retrofitting and modernization services
- Service programs and contracts

You can find detailed information on our range of services in the service catalog web page:

support.industry.siemens.com/cs/sc

Industry Online Support app

You will receive optimum support wherever you are with the "Siemens Industry Online Support" app. The app is available for iOS and Android:

support.industry.siemens.com/cs/ww/en/sc/2067

20. Appendix

20.1. Links and literature

Table 20-1

	Subject
\1\	Siemens Industry Online Support https://support.industry.siemens.com
\2\	Download page of the entry https://support.industry.siemens.com/cs/ww/en/view/109973672
\3\	SIMATIC PCS 7 standard architectures (V10.0 V9.1 / V9.0 / V8.2 / V8.1 / V8.0 / V7.1 / V7.0) https://support.industry.siemens.com/cs/ww/en/view/32201963
\4\	SIMATIC PCS 7 technical documentation – Manuals collection https://support.industry.siemens.com/cs/ww/en/view/109972320
\5\	SIMATIC Process Control System PCS 7 – PC Configuration (V10.0) https://support.industry.siemens.com/cs/ww/en/view/109973495
\6\	SIMATIC Process Control System PCS 7 Licenses and configuration limits (V10.0) https://support.industry.siemens.com/cs/ww/en/view/109973493
\7\	PROFINET in Process Automation with SIMATIC PCS 7 https://support.industry.siemens.com/cs/ww/en/view/72887082

20.2. Document history

Table 20-2

Version	Date	Change
V1.0	07/2016	First edition V8.2
V2.0	11/2017	Complete revision of SIMATIC PCS 7 V9.0
V2.1	10/2018	Section 6.3: Parts list completed Section 15.4.2: Note added below the table "Parts list for concepts 2 and 3". Section 15.4.3: Added notes below the table "Parts list for concept 4".
V2.2	03/2019	Section 17.8: Power supply system SITOP 8600 extended by: USV module UPS8600 BAT8600 LiFePO2 battery module BAT8600 Pb battery module
V3.0	11/2021	Complete revision of SIMATIC PCS 7 V9.1
V4.0	08/2024	Complete revision of SIMATIC PCS 7 V10
V4.1	09/2024	Chapter 16.0: Product Portfolio Added Chapters 16.1 – 16.8: Addition of the SITOP PSU8400 module in circuit diagrams and parts list
V4.2	05/2025	Chapter 16.5: Newly added due to new product SEL1600