

Supplier's declaration of conformity

Document No.: 667.DCO.BOD.40.2205.006



As required by the following Notices:

- > *Radiocommunications (Compliance Labelling - Devices) Notice 2014* made under section 182 of the *Radiocommunications Act 1992*;
- > *Radiocommunications Labelling (Electromagnetic Compatibility) Notice 2017* made under section 182 of the *Radiocommunications Act 1992*
- > *Radiocommunications (Compliance Labelling – Electromagnetic Radiation) Notice 2014* made under section 182 of the *Radiocommunications Act 1992* and
- > *Telecommunications (Labelling Notice for Customer Equipment and Customer Cabling) Instrument 2015* made under section 407 of the *Telecommunications Act 1997*.

Instructions for completion

- > **Do not return this form to the ACMA.** This completed form must be retained by the supplier as part of the documentation required for the compliance records and must be made available for inspection by the ACMA when requested.

Supplier's details (manufacturer, importer or authorised agent)

Company Name (OR INDIVIDUAL)

SIEMENS LTD

ACN/ARBN

OR

New Zealand IRDN

Street Address (AUSTRALIAN or NEW ZEALAND)

885 Mountain Highway
Bayswater
Victoria 3153

Product details and date of manufacture

Product description – name, type/model and test report

Designation G120X	MLFB	Description
G120X (230V,IP20,0.75kW,UF,USS,Blanc,3C2)	6SL3220-1YC10-0UB0	CONVERTER
G120X (230V,IP20,0.75kW,UF,PN,Blanc,3C2)	6SL3220-1YC10-0UF0	CONVERTER
G120X (230V,IP20,0.75kW,UF,DP,Blanc,3C2)	6SL3220-1YC10-0UP0	CONVERTER
G120X (230V,IP20,0.75kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC10-1UB0	CONVERTER
G120X (230V,IP20,0.75kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC10-1UF0	CONVERTER
G120X (230V,IP20,0.75kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC10-1UP0	CONVERTER
G120X (230V,IP20,1.1kW,UF,USS,Blanc,3C2)	6SL3220-1YC12-0UB0	CONVERTER
G120X (230V,IP20,1.1kW,UF,PN,Blanc,3C2)	6SL3220-1YC12-0UF0	CONVERTER
G120X (230V,IP20,1.1kW,UF,DP,Blanc,3C2)	6SL3220-1YC12-0UP0	CONVERTER
G120X (230V,IP20,1.1kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC12-1UB0	CONVERTER

G120X (230V,IP20,1.1kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC12-1UF0	CONVERTER
G120X (230V,IP20,1.1kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC12-1UP0	CONVERTER
G120X (230V,IP20,1.5kW,UF,USS,Blanc,3C2)	6SL3220-1YC14-0UB0	CONVERTER
G120X (230V,IP20,1.5kW,UF,PN,Blanc,3C2)	6SL3220-1YC14-0UF0	CONVERTER
G120X (230V,IP20,1.5kW,UF,DP,Blanc,3C2)	6SL3220-1YC14-0UP0	CONVERTER
G120X (230V,IP20,1.5kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC14-1UB0	CONVERTER
G120X (230V,IP20,1.5kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC14-1UF0	CONVERTER
G120X (230V,IP20,1.5kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC14-1UP0	CONVERTER
G120X (230V,IP20,2.2kW,UF,USS,Blanc,3C2)	6SL3220-1YC16-0UB0	CONVERTER
G120X (230V,IP20,2.2kW,UF,PN,Blanc,3C2)	6SL3220-1YC16-0UF0	CONVERTER
G120X (230V,IP20,2.2kW,UF,DP,Blanc,3C2)	6SL3220-1YC16-0UP0	CONVERTER
G120X (230V,IP20,2.2kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC16-1UB0	CONVERTER
G120X (230V,IP20,2.2kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC16-1UF0	CONVERTER
G120X (230V,IP20,2.2kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC16-1UP0	CONVERTER
G120X (230V,IP20,3kW,UF,USS,Blanc,3C2)	6SL3220-1YC18-0UB0	CONVERTER
G120X (230V,IP20,3kW,UF,PN,Blanc,3C2)	6SL3220-1YC18-0UF0	CONVERTER
G120X (230V,IP20,3kW,UF,DP,Blanc,3C2)	6SL3220-1YC18-0UP0	CONVERTER
G120X (230V,IP20,3kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC18-1UB0	CONVERTER
G120X (230V,IP20,3kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC18-1UF0	CONVERTER
G120X (230V,IP20,3kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC18-1UP0	CONVERTER
G120X (230V,IP20,4kW,UF,USS,Blanc,3C2)	6SL3220-1YC20-0UB0	CONVERTER
G120X (230V,IP20,4kW,UF,PN,Blanc,3C2)	6SL3220-1YC20-0UF0	CONVERTER
G120X (230V,IP20,4kW,UF,DP,Blanc,3C2)	6SL3220-1YC20-0UP0	CONVERTER
G120X (230V,IP20,4kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC20-1UB0	CONVERTER
G120X (230V,IP20,4kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC20-1UF0	CONVERTER
G120X (230V,IP20,4kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC20-1UP0	CONVERTER
G120X (230V,IP20,5.5kW,UF,USS,Blanc,3C2)	6SL3220-1YC22-0UB0	CONVERTER
G120X (230V,IP20,5.5kW,UF,PN,Blanc,3C2)	6SL3220-1YC22-0UF0	CONVERTER
G120X (230V,IP20,5.5kW,UF,DP,Blanc,3C2)	6SL3220-1YC22-0UP0	CONVERTER
G120X (230V,IP20,5.5kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC22-1UB0	CONVERTER
G120X (230V,IP20,5.5kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC22-1UF0	CONVERTER
G120X (230V,IP20,5.5kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC22-1UP0	CONVERTER
G120X (230V,IP20,7.5kW,UF,USS,Blanc,3C2)	6SL3220-1YC24-0UB0	CONVERTER
G120X (230V,IP20,7.5kW,UF,PN,Blanc,3C2)	6SL3220-1YC24-0UF0	CONVERTER
G120X (230V,IP20,7.5kW,UF,DP,Blanc,3C2)	6SL3220-1YC24-0UP0	CONVERTER
G120X (230V,IP20,7.5kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC24-1UB0	CONVERTER
G120X (230V,IP20,7.5kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC24-1UF0	CONVERTER
G120X (230V,IP20,7.5kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC24-1UP0	CONVERTER
G120X (230V,IP20,11kW,UF,USS,Blanc,3C2)	6SL3220-1YC26-0UB0	CONVERTER
G120X (230V,IP20,11kW,UF,PN,Blanc,3C2)	6SL3220-1YC26-0UF0	CONVERTER
G120X (230V,IP20,11kW,UF,DP,Blanc,3C2)	6SL3220-1YC26-0UP0	CONVERTER
G120X (230V,IP20,11kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC26-1UB0	CONVERTER
G120X (230V,IP20,11kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC26-1UF0	CONVERTER
G120X (230V,IP20,11kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC26-1UP0	CONVERTER

G120X (230V,IP20,15kW,UF,USS,Blanc,3C2)	6SL3220-1YC28-0UB0	CONVERTER
G120X (230V,IP20,15kW,UF,PN,Blanc,3C2)	6SL3220-1YC28-0UF0	CONVERTER
G120X (230V,IP20,15kW,UF,DP,Blanc,3C2)	6SL3220-1YC28-0UP0	CONVERTER
G120X (230V,IP20,15kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC28-1UB0	CONVERTER
G120X (230V,IP20,15kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC28-1UF0	CONVERTER
G120X (230V,IP20,15kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC28-1UP0	CONVERTER
G120X (230V,IP20,18,5kW,UF,USS,Blanc,3C2)	6SL3220-1YC30-0UB0	CONVERTER
G120X (230V,IP20,18,5kW,UF,PN,Blanc,3C2)	6SL3220-1YC30-0UF0	CONVERTER
G120X (230V,IP20,18,5kW,UF,DP,Blanc,3C2)	6SL3220-1YC30-0UP0	CONVERTER
G120X (230V,IP20,18,5kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC30-1UB0	CONVERTER
G120X (230V,IP20,18,5kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC30-1UF0	CONVERTER
G120X (230V,IP20,18,5kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC30-1UP0	CONVERTER
G120X (230V,IP20,22kW,UF,USS,Blanc,3C2)	6SL3220-1YC32-0UB0	CONVERTER
G120X (230V,IP20,22kW,UF,PN,Blanc,3C2)	6SL3220-1YC32-0UF0	CONVERTER
G120X (230V,IP20,22kW,UF,DP,Blanc,3C2)	6SL3220-1YC32-0UP0	CONVERTER
G120X (230V,IP20,22kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC32-1UB0	CONVERTER
G120X (230V,IP20,22kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC32-1UF0	CONVERTER
G120X (230V,IP20,22kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC32-1UP0	CONVERTER
G120X (230V,IP20,30kW,UF,USS,Blanc,3C2)	6SL3220-1YC34-0UB0	CONVERTER
G120X (230V,IP20,30kW,UF,PN,Blanc,3C2)	6SL3220-1YC34-0UF0	CONVERTER
G120X (230V,IP20,30kW,UF,DP,Blanc,3C2)	6SL3220-1YC34-0UP0	CONVERTER
G120X (230V,IP20,30kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC34-1UB0	CONVERTER
G120X (230V,IP20,30kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC34-1UF0	CONVERTER
G120X (230V,IP20,30kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC34-1UP0	CONVERTER
G120X (230V,IP20,37kW,UF,USS,Blanc,3C2)	6SL3220-1YC36-0UB0	CONVERTER
G120X (230V,IP20,37kW,UF,PN,Blanc,3C2)	6SL3220-1YC36-0UF0	CONVERTER
G120X (230V,IP20,37kW,UF,DP,Blanc,3C2)	6SL3220-1YC36-0UP0	CONVERTER
G120X (230V,IP20,37kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC36-1UB0	CONVERTER
G120X (230V,IP20,37kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC36-1UF0	CONVERTER
G120X (230V,IP20,37kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC36-1UP0	CONVERTER
G120X (230V,IP20,45kW,UF,USS,Blanc,3C2)	6SL3220-1YC38-0UB0	CONVERTER
G120X (230V,IP20,45kW,UF,PN,Blanc,3C2)	6SL3220-1YC38-0UF0	CONVERTER
G120X (230V,IP20,45kW,UF,DP,Blanc,3C2)	6SL3220-1YC38-0UP0	CONVERTER
G120X (230V,IP20,45kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC38-1UB0	CONVERTER
G120X (230V,IP20,45kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC38-1UF0	CONVERTER
G120X (230V,IP20,45kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC38-1UP0	CONVERTER
G120X (230V,IP20,55kW,UF,USS,Blanc,3C2)	6SL3220-1YC40-0UB0	CONVERTER
G120X (230V,IP20,55kW,UF,PN,Blanc,3C2)	6SL3220-1YC40-0UF0	CONVERTER
G120X (230V,IP20,55kW,UF,DP,Blanc,3C2)	6SL3220-1YC40-0UP0	CONVERTER
G120X (230V,IP20,55kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YC40-1UB0	CONVERTER
G120X (230V,IP20,55kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YC40-1UF0	CONVERTER
G120X (230V,IP20,55kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YC40-1UP0	CONVERTER
G120X (400V,IP20,0.75kW,C2,USS,Blanc,3C2)	6SL3220-1YE10-0AB0	CONVERTER
G120X (400V,IP20,0.75kW,C2,PN,Blanc,3C2)	6SL3220-1YE10-0AF0	CONVERTER

G120X (400V,IP20,0.75kW,C2,DP,Blanc,3C2)	6SL3220-1YE10-0AP0	CONVERTER
G120X (400V,IP20,0.75kW,UF,USS,Blanc,3C2)	6SL3220-1YE10-0UB0	CONVERTER
G120X (400V,IP20,0.75kW,UF,PN,Blanc,3C2)	6SL3220-1YE10-0UF0	CONVERTER
G120X (400V,IP20,0.75kW,UF,DP,Blanc,3C2)	6SL3220-1YE10-0UP0	CONVERTER
G120X (400V,IP20,0.75kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE10-1AB0	CONVERTER
G120X (400V,IP20,0.75kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE10-1AF0	CONVERTER
G120X (400V,IP20,0.75kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE10-1AP0	CONVERTER
G120X (400V,IP20,0.75kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE10-1UB0	CONVERTER
G120X (400V,IP20,0.75kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE10-1UF0	CONVERTER
G120X (400V,IP20,0.75kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE10-1UP0	CONVERTER
G120X (400V,IP20,1.1kW,C2,USS,Blanc,3C2)	6SL3220-1YE12-0AB0	CONVERTER
G120X (400V,IP20,1.1kW,C2,PN,Blanc,3C2)	6SL3220-1YE12-0AF0	CONVERTER
G120X (400V,IP20,1.1kW,C2,DP,Blanc,3C2)	6SL3220-1YE12-0AP0	CONVERTER
G120X (400V,IP20,1.1kW,UF,USS,Blanc,3C2)	6SL3220-1YE12-0UB0	CONVERTER
G120X (400V,IP20,1.1kW,UF,PN,Blanc,3C2)	6SL3220-1YE12-0UF0	CONVERTER
G120X (400V,IP20,1.1kW,UF,DP,Blanc,3C2)	6SL3220-1YE12-0UP0	CONVERTER
G120X (400V,IP20,1.1kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE12-1AB0	CONVERTER
G120X (400V,IP20,1.1kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE12-1AF0	CONVERTER
G120X (400V,IP20,1.1kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE12-1AP0	CONVERTER
G120X (400V,IP20,1.1kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE12-1UB0	CONVERTER
G120X (400V,IP20,1.1kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE12-1UF0	CONVERTER
G120X (400V,IP20,1.1kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE12-1UP0	CONVERTER
G120X (400V,IP20,1.5kW,C2,USS,Blanc,3C2)	6SL3220-1YE14-0AB0	CONVERTER
G120X (400V,IP20,1.5kW,C2,PN,Blanc,3C2)	6SL3220-1YE14-0AF0	CONVERTER
G120X (400V,IP20,1.5kW,C2,DP,Blanc,3C2)	6SL3220-1YE14-0AP0	CONVERTER
G120X (400V,IP20,1.5kW,UF,USS,Blanc,3C2)	6SL3220-1YE14-0UB0	CONVERTER
G120X (400V,IP20,1.5kW,UF,PN,Blanc,3C2)	6SL3220-1YE14-0UF0	CONVERTER
G120X (400V,IP20,1.5kW,UF,DP,Blanc,3C2)	6SL3220-1YE14-0UP0	CONVERTER
G120X (400V,IP20,1.5kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE14-1AB0	CONVERTER
G120X (400V,IP20,1.5kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE14-1AF0	CONVERTER
G120X (400V,IP20,1.5kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE14-1AP0	CONVERTER
G120X (400V,IP20,1.5kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE14-1UB0	CONVERTER
G120X (400V,IP20,1.5kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE14-1UF0	CONVERTER
G120X (400V,IP20,1.5kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE14-1UP0	CONVERTER
G120X (400V,IP20,2.2kW,C2,USS,Blanc,3C2)	6SL3220-1YE16-0AB0	CONVERTER
G120X (400V,IP20,2.2kW,C2,PN,Blanc,3C2)	6SL3220-1YE16-0AF0	CONVERTER
G120X (400V,IP20,2.2kW,C2,DP,Blanc,3C2)	6SL3220-1YE16-0AP0	CONVERTER
G120X (400V,IP20,2.2kW,UF,USS,Blanc,3C2)	6SL3220-1YE16-0UB0	CONVERTER
G120X (400V,IP20,2.2kW,UF,PN,Blanc,3C2)	6SL3220-1YE16-0UF0	CONVERTER
G120X (400V,IP20,2.2kW,UF,DP,Blanc,3C2)	6SL3220-1YE16-0UP0	CONVERTER
G120X (400V,IP20,2.2kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE16-1AB0	CONVERTER
G120X (400V,IP20,2.2kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE16-1AF0	CONVERTER
G120X (400V,IP20,2.2kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE16-1AP0	CONVERTER
G120X (400V,IP20,2.2kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE16-1UB0	CONVERTER

G120X (400V,IP20,2.2kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE16-1UF0	CONVERTER
G120X (400V,IP20,2.2kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE16-1UP0	CONVERTER
G120X (400V,IP20,3kW,C2,USS,Blanc,3C2)	6SL3220-1YE18-0AB0	CONVERTER
G120X (400V,IP20,3kW,C2,PN,Blanc,3C2)	6SL3220-1YE18-0AF0	CONVERTER
G120X (400V,IP20,3kW,C2,DP,Blanc,3C2)	6SL3220-1YE18-0AP0	CONVERTER
G120X (400V,IP20,3kW,UF,USS,Blanc,3C2)	6SL3220-1YE18-0UB0	CONVERTER
G120X (400V,IP20,3kW,UF,PN,Blanc,3C2)	6SL3220-1YE18-0UF0	CONVERTER
G120X (400V,IP20,3kW,UF,DP,Blanc,3C2)	6SL3220-1YE18-0UP0	CONVERTER
G120X (400V,IP20,3kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE18-1AB0	CONVERTER
G120X (400V,IP20,3kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE18-1AF0	CONVERTER
G120X (400V,IP20,3kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE18-1AP0	CONVERTER
G120X (400V,IP20,3kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE18-1UB0	CONVERTER
G120X (400V,IP20,3kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE18-1UF0	CONVERTER
G120X (400V,IP20,3kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE18-1UP0	CONVERTER
G120X (400V,IP20,4kW,C2,USS,Blanc,3C2)	6SL3220-1YE20-0AB0	CONVERTER
G120X (400V,IP20,4kW,C2,PN,Blanc,3C2)	6SL3220-1YE20-0AF0	CONVERTER
G120X (400V,IP20,4kW,C2,DP,Blanc,3C2)	6SL3220-1YE20-0AP0	CONVERTER
G120X (400V,IP20,4kW,UF,USS,Blanc,3C2)	6SL3220-1YE20-0UB0	CONVERTER
G120X (400V,IP20,4kW,UF,PN,Blanc,3C2)	6SL3220-1YE20-0UF0	CONVERTER
G120X (400V,IP20,4kW,UF,DP,Blanc,3C2)	6SL3220-1YE20-0UP0	CONVERTER
G120X (400V,IP20,4kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE20-1AB0	CONVERTER
G120X (400V,IP20,4kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE20-1AF0	CONVERTER
G120X (400V,IP20,4kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE20-1AP0	CONVERTER
G120X (400V,IP20,4kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE20-1UB0	CONVERTER
G120X (400V,IP20,4kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE20-1UF0	CONVERTER
G120X (400V,IP20,4kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE20-1UP0	CONVERTER
G120X (400V,IP20,5.5kW,C2,USS,Blanc,3C2)	6SL3220-1YE22-0AB0	CONVERTER
G120X (400V,IP20,5.5kW,C2,PN,Blanc,3C2)	6SL3220-1YE22-0AF0	CONVERTER
G120X (400V,IP20,5.5kW,C2,DP,Blanc,3C2)	6SL3220-1YE22-0AP0	CONVERTER
G120X (400V,IP20,5.5kW,UF,USS,Blanc,3C2)	6SL3220-1YE22-0UB0	CONVERTER
G120X (400V,IP20,5.5kW,UF,PN,Blanc,3C2)	6SL3220-1YE22-0UF0	CONVERTER
G120X (400V,IP20,5.5kW,UF,DP,Blanc,3C2)	6SL3220-1YE22-0UP0	CONVERTER
G120X (400V,IP20,5.5kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE22-1AB0	CONVERTER
G120X (400V,IP20,5.5kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE22-1AF0	CONVERTER
G120X (400V,IP20,5.5kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE22-1AP0	CONVERTER
G120X (400V,IP20,5.5kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE22-1UB0	CONVERTER
G120X (400V,IP20,5.5kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE22-1UF0	CONVERTER
G120X (400V,IP20,5.5kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE22-1UP0	CONVERTER
G120X (400V,IP20,7.5kW,C2,USS,Blanc,3C2)	6SL3220-1YE24-0AB0	CONVERTER
G120X (400V,IP20,7.5kW,C2,PN,Blanc,3C2)	6SL3220-1YE24-0AF0	CONVERTER
G120X (400V,IP20,7.5kW,C2,DP,Blanc,3C2)	6SL3220-1YE24-0AP0	CONVERTER
G120X (400V,IP20,7.5kW,UF,USS,Blanc,3C2)	6SL3220-1YE24-0UB0	CONVERTER
G120X (400V,IP20,7.5kW,UF,PN,Blanc,3C2)	6SL3220-1YE24-0UF0	CONVERTER
G120X (400V,IP20,7.5kW,UF,DP,Blanc,3C2)	6SL3220-1YE24-0UP0	CONVERTER

G120X (400V,IP20,7.5kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE24-1AB0	CONVERTER
G120X (400V,IP20,7.5kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE24-1AF0	CONVERTER
G120X (400V,IP20,7.5kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE24-1AP0	CONVERTER
G120X (400V,IP20,7.5kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE24-1UB0	CONVERTER
G120X (400V,IP20,7.5kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE24-1UF0	CONVERTER
G120X (400V,IP20,7.5kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE24-1UP0	CONVERTER
G120X (400V,IP20,11kW,C2,USS,Blanc,3C2)	6SL3220-1YE26-0AB0	CONVERTER
G120X (400V,IP20,11kW,C2,PN,Blanc,3C2)	6SL3220-1YE26-0AF0	CONVERTER
G120X (400V,IP20,11kW,C2,DP,Blanc,3C2)	6SL3220-1YE26-0AP0	CONVERTER
G120X (400V,IP20,11kW,UF,USS,Blanc,3C2)	6SL3220-1YE26-0UB0	CONVERTER
G120X (400V,IP20,11kW,UF,PN,Blanc,3C2)	6SL3220-1YE26-0UF0	CONVERTER
G120X (400V,IP20,11kW,UF,DP,Blanc,3C2)	6SL3220-1YE26-0UP0	CONVERTER
G120X (400V,IP20,11kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE26-1AB0	CONVERTER
G120X (400V,IP20,11kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE26-1AF0	CONVERTER
G120X (400V,IP20,11kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE26-1AP0	CONVERTER
G120X (400V,IP20,11kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE26-1UB0	CONVERTER
G120X (400V,IP20,11kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE26-1UF0	CONVERTER
G120X (400V,IP20,11kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE26-1UP0	CONVERTER
G120X (400V,IP20,15kW,C2,USS,Blanc,3C2)	6SL3220-1YE28-0AB0	CONVERTER
G120X (400V,IP20,15kW,C2,PN,Blanc,3C2)	6SL3220-1YE28-0AF0	CONVERTER
G120X (400V,IP20,15kW,C2,DP,Blanc,3C2)	6SL3220-1YE28-0AP0	CONVERTER
G120X (400V,IP20,15kW,UF,USS,Blanc,3C2)	6SL3220-1YE28-0UB0	CONVERTER
G120X (400V,IP20,15kW,UF,PN,Blanc,3C2)	6SL3220-1YE28-0UF0	CONVERTER
G120X (400V,IP20,15kW,UF,DP,Blanc,3C2)	6SL3220-1YE28-0UP0	CONVERTER
G120X (400V,IP20,15kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE28-1AB0	CONVERTER
G120X (400V,IP20,15kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE28-1AF0	CONVERTER
G120X (400V,IP20,15kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE28-1AP0	CONVERTER
G120X (400V,IP20,15kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE28-1UB0	CONVERTER
G120X (400V,IP20,15kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE28-1UF0	CONVERTER
G120X (400V,IP20,15kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE28-1UP0	CONVERTER
G120X (400V,IP20,18,5kW,C2,USS,Blanc,3C2)	6SL3220-1YE30-0AB0	CONVERTER
G120X (400V,IP20,18,5kW,C2,PN,Blanc,3C2)	6SL3220-1YE30-0AF0	CONVERTER
G120X (400V,IP20,18,5kW,C2,DP,Blanc,3C2)	6SL3220-1YE30-0AP0	CONVERTER
G120X (400V,IP20,18,5kW,UF,USS,Blanc,3C2)	6SL3220-1YE30-0UB0	CONVERTER
G120X (400V,IP20,18,5kW,UF,PN,Blanc,3C2)	6SL3220-1YE30-0UF0	CONVERTER
G120X (400V,IP20,18,5kW,UF,DP,Blanc,3C2)	6SL3220-1YE30-0UP0	CONVERTER
G120X (400V,IP20,18,5kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE30-1AB0	CONVERTER
G120X (400V,IP20,18,5kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE30-1AF0	CONVERTER
G120X (400V,IP20,18,5kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE30-1AP0	CONVERTER
G120X (400V,IP20,18,5kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE30-1UB0	CONVERTER
G120X (400V,IP20,18,5kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE30-1UF0	CONVERTER
G120X (400V,IP20,18,5kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE30-1UP0	CONVERTER
G120X (400V,IP20,22kW,C2,USS,Blanc,3C2)	6SL3220-1YE32-0AB0	CONVERTER
G120X (400V,IP20,22kW,C2,PN,Blanc,3C2)	6SL3220-1YE32-0AF0	CONVERTER

G120X (400V,IP20,22kW,C2,DP,Blanc,3C2)	6SL3220-1YE32-0AP0	CONVERTER
G120X (400V,IP20,22kW,UF,USS,Blanc,3C2)	6SL3220-1YE32-0UB0	CONVERTER
G120X (400V,IP20,22kW,UF,PN,Blanc,3C2)	6SL3220-1YE32-0UF0	CONVERTER
G120X (400V,IP20,22kW,UF,DP,Blanc,3C2)	6SL3220-1YE32-0UP0	CONVERTER
G120X (400V,IP20,22kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE32-1AB0	CONVERTER
G120X (400V,IP20,22kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE32-1AF0	CONVERTER
G120X (400V,IP20,22kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE32-1AP0	CONVERTER
G120X (400V,IP20,22kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE32-1UB0	CONVERTER
G120X (400V,IP20,22kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE32-1UF0	CONVERTER
G120X (400V,IP20,22kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE32-1UP0	CONVERTER
G120X (400V,IP20,30kW,C2,USS,Blanc,3C2)	6SL3220-1YE34-0AB0	CONVERTER
G120X (400V,IP20,30kW,C2,PN,Blanc,3C2)	6SL3220-1YE34-0AF0	CONVERTER
G120X (400V,IP20,30kW,C2,DP,Blanc,3C2)	6SL3220-1YE34-0AP0	CONVERTER
G120X (400V,IP20,30kW,UF,USS,Blanc,3C2)	6SL3220-1YE34-0UB0	CONVERTER
G120X (400V,IP20,30kW,UF,PN,Blanc,3C2)	6SL3220-1YE34-0UF0	CONVERTER
G120X (400V,IP20,30kW,UF,DP,Blanc,3C2)	6SL3220-1YE34-0UP0	CONVERTER
G120X (400V,IP20,30kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE34-1AB0	CONVERTER
G120X (400V,IP20,30kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE34-1AF0	CONVERTER
G120X (400V,IP20,30kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE34-1AP0	CONVERTER
G120X (400V,IP20,30kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE34-1UB0	CONVERTER
G120X (400V,IP20,30kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE34-1UF0	CONVERTER
G120X (400V,IP20,30kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE34-1UP0	CONVERTER
G120X (400V,IP20,37kW,C2,USS,Blanc,3C2)	6SL3220-1YE36-0AB0	CONVERTER
G120X (400V,IP20,37kW,C2,PN,Blanc,3C2)	6SL3220-1YE36-0AF0	CONVERTER
G120X (400V,IP20,37kW,C2,DP,Blanc,3C2)	6SL3220-1YE36-0AP0	CONVERTER
G120X (400V,IP20,37kW,UF,USS,Blanc,3C2)	6SL3220-1YE36-0UB0	CONVERTER
G120X (400V,IP20,37kW,UF,PN,Blanc,3C2)	6SL3220-1YE36-0UF0	CONVERTER
G120X (400V,IP20,37kW,UF,DP,Blanc,3C2)	6SL3220-1YE36-0UP0	CONVERTER
G120X (400V,IP20,37kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE36-1AB0	CONVERTER
G120X (400V,IP20,37kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE36-1AF0	CONVERTER
G120X (400V,IP20,37kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE36-1AP0	CONVERTER
G120X (400V,IP20,37kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE36-1UB0	CONVERTER
G120X (400V,IP20,37kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE36-1UF0	CONVERTER
G120X (400V,IP20,37kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE36-1UP0	CONVERTER
G120X (400V,IP20,45kW,C2,USS,Blanc,3C2)	6SL3220-1YE38-0AB0	CONVERTER
G120X (400V,IP20,45kW,C2,PN,Blanc,3C2)	6SL3220-1YE38-0AF0	CONVERTER
G120X (400V,IP20,45kW,C2,DP,Blanc,3C2)	6SL3220-1YE38-0AP0	CONVERTER
G120X (400V,IP20,45kW,UF,USS,Blanc,3C2)	6SL3220-1YE38-0UB0	CONVERTER
G120X (400V,IP20,45kW,UF,PN,Blanc,3C2)	6SL3220-1YE38-0UF0	CONVERTER
G120X (400V,IP20,45kW,UF,DP,Blanc,3C2)	6SL3220-1YE38-0UP0	CONVERTER
G120X (400V,IP20,45kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE38-1AB0	CONVERTER
G120X (400V,IP20,45kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE38-1AF0	CONVERTER
G120X (400V,IP20,45kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE38-1AP0	CONVERTER
G120X (400V,IP20,45kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE38-1UB0	CONVERTER

G120X (400V,IP20,45kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE38-1UF0	CONVERTER
G120X (400V,IP20,45kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE38-1UP0	CONVERTER
G120X (400V,IP20,55kW,C2,USS,Blanc,3C2)	6SL3220-1YE40-0AB0	CONVERTER
G120X (400V,IP20,55kW,C2,PN,Blanc,3C2)	6SL3220-1YE40-0AF0	CONVERTER
G120X (400V,IP20,55kW,C2,DP,Blanc,3C2)	6SL3220-1YE40-0AP0	CONVERTER
G120X (400V,IP20,55kW,UF,USS,Blanc,3C2)	6SL3220-1YE40-0UB0	CONVERTER
G120X (400V,IP20,55kW,UF,PN,Blanc,3C2)	6SL3220-1YE40-0UF0	CONVERTER
G120X (400V,IP20,55kW,UF,DP,Blanc,3C2)	6SL3220-1YE40-0UP0	CONVERTER
G120X (400V,IP20,55kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE40-1AB0	CONVERTER
G120X (400V,IP20,55kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE40-1AF0	CONVERTER
G120X (400V,IP20,55kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE40-1AP0	CONVERTER
G120X (400V,IP20,55kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE40-1UB0	CONVERTER
G120X (400V,IP20,55kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE40-1UF0	CONVERTER
G120X (400V,IP20,55kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE40-1UP0	CONVERTER
G120X (400V,IP20,75kW,C2,USS,Blanc,3C2)	6SL3220-1YE42-0AB0	CONVERTER
G120X (400V,IP20,75kW,C2,PN,Blanc,3C2)	6SL3220-1YE42-0AF0	CONVERTER
G120X (400V,IP20,75kW,C2,DP,Blanc,3C2)	6SL3220-1YE42-0AP0	CONVERTER
G120X (400V,IP20,75kW,UF,USS,Blanc,3C2)	6SL3220-1YE42-0UB0	CONVERTER
G120X (400V,IP20,75kW,UF,PN,Blanc,3C2)	6SL3220-1YE42-0UF0	CONVERTER
G120X (400V,IP20,75kW,UF,DP,Blanc,3C2)	6SL3220-1YE42-0UP0	CONVERTER
G120X (400V,IP20,75kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE42-1AB0	CONVERTER
G120X (400V,IP20,75kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE42-1AF0	CONVERTER
G120X (400V,IP20,75kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE42-1AP0	CONVERTER
G120X (400V,IP20,75kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE42-1UB0	CONVERTER
G120X (400V,IP20,75kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE42-1UF0	CONVERTER
G120X (400V,IP20,75kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE42-1UP0	CONVERTER
G120X (400V,IP20,90kW,C2,USS,Blanc,3C2)	6SL3220-1YE44-0AB0	CONVERTER
G120X (400V,IP20,90kW,C2,PN,Blanc,3C2)	6SL3220-1YE44-0AF0	CONVERTER
G120X (400V,IP20,90kW,C2,DP,Blanc,3C2)	6SL3220-1YE44-0AP0	CONVERTER
G120X (400V,IP20,90kW,UF,USS,Blanc,3C2)	6SL3220-1YE44-0UB0	CONVERTER
G120X (400V,IP20,90kW,UF,PN,Blanc,3C2)	6SL3220-1YE44-0UF0	CONVERTER
G120X (400V,IP20,90kW,UF,DP,Blanc,3C2)	6SL3220-1YE44-0UP0	CONVERTER
G120X (400V,IP20,90kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE44-1AB0	CONVERTER
G120X (400V,IP20,90kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE44-1AF0	CONVERTER
G120X (400V,IP20,90kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE44-1AP0	CONVERTER
G120X (400V,IP20,90kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE44-1UB0	CONVERTER
G120X (400V,IP20,90kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE44-1UF0	CONVERTER
G120X (400V,IP20,90kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE44-1UP0	CONVERTER
G120X (400V,IP20,110kW,C2,USS,Blanc,3C2)	6SL3220-1YE46-0AB0	CONVERTER
G120X (400V,IP20,110kW,C2,PN,Blanc,3C2)	6SL3220-1YE46-0AF0	CONVERTER
G120X (400V,IP20,110kW,C2,DP,Blanc,3C2)	6SL3220-1YE46-0AP0	CONVERTER
G120X (400V,IP20,110kW,UF,USS,Blanc,3C2)	6SL3220-1YE46-0UB0	CONVERTER
G120X (400V,IP20,110kW,UF,PN,Blanc,3C2)	6SL3220-1YE46-0UF0	CONVERTER
G120X (400V,IP20,110kW,UF,DP,Blanc,3C2)	6SL3220-1YE46-0UP0	CONVERTER

G120X (400V,IP20,110kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE46-1AB0	CONVERTER
G120X (400V,IP20,110kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE46-1AF0	CONVERTER
G120X (400V,IP20,110kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE46-1AP0	CONVERTER
G120X (400V,IP20,110kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE46-1UB0	CONVERTER
G120X (400V,IP20,110kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE46-1UF0	CONVERTER
G120X (400V,IP20,110kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE46-1UP0	CONVERTER
G120X (400V,IP20,132kW,C2,USS,Blanc,3C2)	6SL3220-1YE48-0AB0	CONVERTER
G120X (400V,IP20,132kW,C2,PN,Blanc,3C2)	6SL3220-1YE48-0AF0	CONVERTER
G120X (400V,IP20,132kW,C2,DP,Blanc,3C2)	6SL3220-1YE48-0AP0	CONVERTER
G120X (400V,IP20,132kW,UF,USS,Blanc,3C2)	6SL3220-1YE48-0UB0	CONVERTER
G120X (400V,IP20,132kW,UF,PN,Blanc,3C2)	6SL3220-1YE48-0UF0	CONVERTER
G120X (400V,IP20,132kW,UF,DP,Blanc,3C2)	6SL3220-1YE48-0UP0	CONVERTER
G120X (400V,IP20,132kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE48-1AB0	CONVERTER
G120X (400V,IP20,132kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE48-1AF0	CONVERTER
G120X (400V,IP20,132kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE48-1AP0	CONVERTER
G120X (400V,IP20,132kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YE48-1UB0	CONVERTER
G120X (400V,IP20,132kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YE48-1UF0	CONVERTER
G120X (400V,IP20,132kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YE48-1UP0	CONVERTER
G120X (400V,IP20,160kW,C2,USS,Blanc,3C2)	6SL3220-1YE50-0AB0	CONVERTER
G120X (400V,IP20,160kW,C2,PN,Blanc,3C2)	6SL3220-1YE50-0AF0	CONVERTER
G120X (400V,IP20,160kW,C2,DP,Blanc,3C2)	6SL3220-1YE50-0AP0	CONVERTER
G120X (400V,IP20,160kW,C3,USS,Blanc,3C2)	6SL3220-1YE50-0CB0	CONVERTER
G120X (400V,IP20,160kW,C3,PN,Blanc,3C2)	6SL3220-1YE50-0CF0	CONVERTER
G120X (400V,IP20,160kW,C3,DP,Blanc,3C2)	6SL3220-1YE50-0CP0	CONVERTER
G120X (400V,IP20,160kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE50-1AB0	CONVERTER
G120X (400V,IP20,160kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE50-1AF0	CONVERTER
G120X (400V,IP20,160kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE50-1AP0	CONVERTER
G120X (400V,IP20,160kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YE50-1CB0	CONVERTER
G120X (400V,IP20,160kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YE50-1CF0	CONVERTER
G120X (400V,IP20,160kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YE50-1CP0	CONVERTER
G120X (400V,IP20,200kW,C2,USS,Blanc,3C2)	6SL3220-1YE52-0AB0	CONVERTER
G120X (400V,IP20,200kW,C2,PN,Blanc,3C2)	6SL3220-1YE52-0AF0	CONVERTER
G120X (400V,IP20,200kW,C2,DP,Blanc,3C2)	6SL3220-1YE52-0AP0	CONVERTER
G120X (400V,IP20,200kW,C3,USS,Blanc,3C2)	6SL3220-1YE52-0CB0	CONVERTER
G120X (400V,IP20,200kW,C3,PN,Blanc,3C2)	6SL3220-1YE52-0CF0	CONVERTER
G120X (400V,IP20,200kW,C3,DP,Blanc,3C2)	6SL3220-1YE52-0CP0	CONVERTER
G120X (400V,IP20,200kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE52-1AB0	CONVERTER
G120X (400V,IP20,200kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE52-1AF0	CONVERTER
G120X (400V,IP20,200kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE52-1AP0	CONVERTER
G120X (400V,IP20,200kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YE52-1CB0	CONVERTER
G120X (400V,IP20,200kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YE52-1CF0	CONVERTER
G120X (400V,IP20,200kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YE52-1CP0	CONVERTER
G120X (400V,IP20,250kW,C2,USS,Blanc,3C2)	6SL3220-1YE54-0AB0	CONVERTER
G120X (400V,IP20,250kW,C2,PN,Blanc,3C2)	6SL3220-1YE54-0AF0	CONVERTER

G120X (400V,IP20,250kW,C2,DP,Blanc,3C2)	6SL3220-1YE54-0AP0	CONVERTER
G120X (400V,IP20,250kW,C3,USS,Blanc,3C2)	6SL3220-1YE54-0CB0	CONVERTER
G120X (400V,IP20,250kW,C3,PN,Blanc,3C2)	6SL3220-1YE54-0CF0	CONVERTER
G120X (400V,IP20,250kW,C3,DP,Blanc,3C2)	6SL3220-1YE54-0CP0	CONVERTER
G120X (400V,IP20,250kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YE54-1AB0	CONVERTER
G120X (400V,IP20,250kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YE54-1AF0	CONVERTER
G120X (400V,IP20,250kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YE54-1AP0	CONVERTER
G120X (400V,IP20,250kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YE54-1CB0	CONVERTER
G120X (400V,IP20,250kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YE54-1CF0	CONVERTER
G120X (400V,IP20,250kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YE54-1CP0	CONVERTER
G120X (400V,IP20,315kW,C3,USS,Blanc,3C2)	6SL3220-1YE56-0CB0	CONVERTER
G120X (400V,IP20,315kW,C3,PN,Blanc,3C2)	6SL3220-1YE56-0CF0	CONVERTER
G120X (400V,IP20,315kW,C3,DP,Blanc,3C2)	6SL3220-1YE56-0CP0	CONVERTER
G120X (400V,IP20,315kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YE56-1CB0	CONVERTER
G120X (400V,IP20,315kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YE56-1CF0	CONVERTER
G120X (400V,IP20,315kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YE56-1CP0	CONVERTER
G120X (400V,IP20,355kW,C3,USS,Blanc,3C2)	6SL3220-1YE58-0CB0	CONVERTER
G120X (400V,IP20,355kW,C3,PN,Blanc,3C2)	6SL3220-1YE58-0CF0	CONVERTER
G120X (400V,IP20,355kW,C3,DP,Blanc,3C2)	6SL3220-1YE58-0CP0	CONVERTER
G120X (400V,IP20,355kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YE58-1CB0	CONVERTER
G120X (400V,IP20,355kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YE58-1CF0	CONVERTER
G120X (400V,IP20,355kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YE58-1CP0	CONVERTER
G120X (400V,IP20,400kW,C3,USS,Blanc,3C2)	6SL3220-1YE60-0CB0	CONVERTER
G120X (400V,IP20,400kW,C3,PN,Blanc,3C2)	6SL3220-1YE60-0CF0	CONVERTER
G120X (400V,IP20,400kW,C3,DP,Blanc,3C2)	6SL3220-1YE60-0CP0	CONVERTER
G120X (400V,IP20,400kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YE60-1CB0	CONVERTER
G120X (400V,IP20,400kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YE60-1CF0	CONVERTER
G120X (400V,IP20,400kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YE60-1CP0	CONVERTER
G120X (400V,IP20,450kW,C3,USS,Blanc,3C2)	6SL3220-1YE62-0CB0	CONVERTER
G120X (400V,IP20,450kW,C3,PN,Blanc,3C2)	6SL3220-1YE62-0CF0	CONVERTER
G120X (400V,IP20,450kW,C3,DP,Blanc,3C2)	6SL3220-1YE62-0CP0	CONVERTER
G120X (400V,IP20,450kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YE62-1CB0	CONVERTER
G120X (400V,IP20,450kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YE62-1CF0	CONVERTER
G120X (400V,IP20,450kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YE62-1CP0	CONVERTER
G120X (400V,IP20,500kW,C3,USS,Blanc,3C2)	6SL3220-1YE64-0CB0	CONVERTER
G120X (400V,IP20,500kW,C3,PN,Blanc,3C2)	6SL3220-1YE64-0CF0	CONVERTER
G120X (400V,IP20,500kW,C3,DP,Blanc,3C2)	6SL3220-1YE64-0CP0	CONVERTER
G120X (400V,IP20,500kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YE64-1CB0	CONVERTER
G120X (400V,IP20,500kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YE64-1CF0	CONVERTER
G120X (400V,IP20,500kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YE64-1CP0	CONVERTER
G120X (400V,IP20,560kW,C3,USS,Blanc,3C2)	6SL3220-1YE66-0CB0	CONVERTER
G120X (400V,IP20,560kW,C3,PN,Blanc,3C2)	6SL3220-1YE66-0CF0	CONVERTER
G120X (400V,IP20,560kW,C3,DP,Blanc,3C2)	6SL3220-1YE66-0CP0	CONVERTER
G120X (400V,IP20,560kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YE66-1CB0	CONVERTER

G120X (400V,IP20,560kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YE66-1CF0	CONVERTER
G120X (400V,IP20,560kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YE66-1CP0	CONVERTER
G120X (690V,IP20,3kW,C2,USS,Blanc,3C2)	6SL3220-1YH18-0AB0	CONVERTER
G120X (690V,IP20,3kW,C2,PN,Blanc,3C2)	6SL3220-1YH18-0AF0	CONVERTER
G120X (690V,IP20,3kW,C2,DP,Blanc,3C2)	6SL3220-1YH18-0AP0	CONVERTER
G120X (690V,IP20,3kW,UF,USS,Blanc,3C2)	6SL3220-1YH18-0UB0	CONVERTER
G120X (690V,IP20,3kW,UF,PN,Blanc,3C2)	6SL3220-1YH18-0UF0	CONVERTER
G120X (690V,IP20,3kW,UF,DP,Blanc,3C2)	6SL3220-1YH18-0UP0	CONVERTER
G120X (690V,IP20,3kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YH18-1AB0	CONVERTER
G120X (690V,IP20,3kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YH18-1AF0	CONVERTER
G120X (690V,IP20,3kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YH18-1AP0	CONVERTER
G120X (690V,IP20,3kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH18-1UB0	CONVERTER
G120X (690V,IP20,3kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH18-1UF0	CONVERTER
G120X (690V,IP20,3kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH18-1UP0	CONVERTER
G120X (690V,IP20,4kW,C2,USS,Blanc,3C2)	6SL3220-1YH20-0AB0	CONVERTER
G120X (690V,IP20,4kW,C2,PN,Blanc,3C2)	6SL3220-1YH20-0AF0	CONVERTER
G120X (690V,IP20,4kW,C2,DP,Blanc,3C2)	6SL3220-1YH20-0AP0	CONVERTER
G120X (690V,IP20,4kW,UF,USS,Blanc,3C2)	6SL3220-1YH20-0UB0	CONVERTER
G120X (690V,IP20,4kW,UF,PN,Blanc,3C2)	6SL3220-1YH20-0UF0	CONVERTER
G120X (690V,IP20,4kW,UF,DP,Blanc,3C2)	6SL3220-1YH20-0UP0	CONVERTER
G120X (690V,IP20,4kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YH20-1AB0	CONVERTER
G120X (690V,IP20,4kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YH20-1AF0	CONVERTER
G120X (690V,IP20,4kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YH20-1AP0	CONVERTER
G120X (690V,IP20,4kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH20-1UB0	CONVERTER
G120X (690V,IP20,4kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH20-1UF0	CONVERTER
G120X (690V,IP20,4kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH20-1UP0	CONVERTER
G120X (690V,IP20,5.5kW,C2,USS,Blanc,3C2)	6SL3220-1YH22-0AB0	CONVERTER
G120X (690V,IP20,5.5kW,C2,PN,Blanc,3C2)	6SL3220-1YH22-0AF0	CONVERTER
G120X (690V,IP20,5.5kW,C2,DP,Blanc,3C2)	6SL3220-1YH22-0AP0	CONVERTER
G120X (690V,IP20,5.5kW,UF,USS,Blanc,3C2)	6SL3220-1YH22-0UB0	CONVERTER
G120X (690V,IP20,5.5kW,UF,PN,Blanc,3C2)	6SL3220-1YH22-0UF0	CONVERTER
G120X (690V,IP20,5.5kW,UF,DP,Blanc,3C2)	6SL3220-1YH22-0UP0	CONVERTER
G120X (690V,IP20,5.5kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YH22-1AB0	CONVERTER
G120X (690V,IP20,5.5kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YH22-1AF0	CONVERTER
G120X (690V,IP20,5.5kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YH22-1AP0	CONVERTER
G120X (690V,IP20,5.5kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH22-1UB0	CONVERTER
G120X (690V,IP20,5.5kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH22-1UF0	CONVERTER
G120X (690V,IP20,5.5kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH22-1UP0	CONVERTER
G120X (690V,IP20,7.5kW,C2,USS,Blanc,3C2)	6SL3220-1YH24-0AB0	CONVERTER
G120X (690V,IP20,7.5kW,C2,PN,Blanc,3C2)	6SL3220-1YH24-0AF0	CONVERTER
G120X (690V,IP20,7.5kW,C2,DP,Blanc,3C2)	6SL3220-1YH24-0AP0	CONVERTER
G120X (690V,IP20,7.5kW,UF,USS,Blanc,3C2)	6SL3220-1YH24-0UB0	CONVERTER
G120X (690V,IP20,7.5kW,UF,PN,Blanc,3C2)	6SL3220-1YH24-0UF0	CONVERTER
G120X (690V,IP20,7.5kW,UF,DP,Blanc,3C2)	6SL3220-1YH24-0UP0	CONVERTER

G120X (690V,IP20,7.5kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YH24-1AB0	CONVERTER
G120X (690V,IP20,7.5kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YH24-1AF0	CONVERTER
G120X (690V,IP20,7.5kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YH24-1AP0	CONVERTER
G120X (690V,IP20,7.5kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH24-1UB0	CONVERTER
G120X (690V,IP20,7.5kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH24-1UF0	CONVERTER
G120X (690V,IP20,7.5kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH24-1UP0	CONVERTER
G120X (690V,IP20,11kW,C2,USS,Blanc,3C2)	6SL3220-1YH26-0AB0	CONVERTER
G120X (690V,IP20,11kW,C2,PN,Blanc,3C2)	6SL3220-1YH26-0AF0	CONVERTER
G120X (690V,IP20,11kW,C2,DP,Blanc,3C2)	6SL3220-1YH26-0AP0	CONVERTER
G120X (690V,IP20,11kW,UF,USS,Blanc,3C2)	6SL3220-1YH26-0UB0	CONVERTER
G120X (690V,IP20,11kW,UF,PN,Blanc,3C2)	6SL3220-1YH26-0UF0	CONVERTER
G120X (690V,IP20,11kW,UF,DP,Blanc,3C2)	6SL3220-1YH26-0UP0	CONVERTER
G120X (690V,IP20,11kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YH26-1AB0	CONVERTER
G120X (690V,IP20,11kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YH26-1AF0	CONVERTER
G120X (690V,IP20,11kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YH26-1AP0	CONVERTER
G120X (690V,IP20,11kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH26-1UB0	CONVERTER
G120X (690V,IP20,11kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH26-1UF0	CONVERTER
G120X (690V,IP20,11kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH26-1UP0	CONVERTER
G120X (690V,IP20,15kW,C2,USS,Blanc,3C2)	6SL3220-1YH28-0AB0	CONVERTER
G120X (690V,IP20,15kW,C2,PN,Blanc,3C2)	6SL3220-1YH28-0AF0	CONVERTER
G120X (690V,IP20,15kW,C2,DP,Blanc,3C2)	6SL3220-1YH28-0AP0	CONVERTER
G120X (690V,IP20,15kW,UF,USS,Blanc,3C2)	6SL3220-1YH28-0UB0	CONVERTER
G120X (690V,IP20,15kW,UF,PN,Blanc,3C2)	6SL3220-1YH28-0UF0	CONVERTER
G120X (690V,IP20,15kW,UF,DP,Blanc,3C2)	6SL3220-1YH28-0UP0	CONVERTER
G120X (690V,IP20,15kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YH28-1AB0	CONVERTER
G120X (690V,IP20,15kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YH28-1AF0	CONVERTER
G120X (690V,IP20,15kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YH28-1AP0	CONVERTER
G120X (690V,IP20,15kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH28-1UB0	CONVERTER
G120X (690V,IP20,15kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH28-1UF0	CONVERTER
G120X (690V,IP20,15kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH28-1UP0	CONVERTER
G120X (690V,IP20,18,5kW,C2,USS,Blanc,3C2)	6SL3220-1YH30-0AB0	CONVERTER
G120X (690V,IP20,18,5kW,C2,PN,Blanc,3C2)	6SL3220-1YH30-0AF0	CONVERTER
G120X (690V,IP20,18,5kW,C2,DP,Blanc,3C2)	6SL3220-1YH30-0AP0	CONVERTER
G120X (690V,IP20,18,5kW,UF,USS,Blanc,3C2)	6SL3220-1YH30-0UB0	CONVERTER
G120X (690V,IP20,18,5kW,UF,PN,Blanc,3C2)	6SL3220-1YH30-0UF0	CONVERTER
G120X (690V,IP20,18,5kW,UF,DP,Blanc,3C2)	6SL3220-1YH30-0UP0	CONVERTER
G120X (690V,IP20,18,5kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YH30-1AB0	CONVERTER
G120X (690V,IP20,18,5kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YH30-1AF0	CONVERTER
G120X (690V,IP20,18,5kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YH30-1AP0	CONVERTER
G120X (690V,IP20,18,5kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH30-1UB0	CONVERTER
G120X (690V,IP20,18,5kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH30-1UF0	CONVERTER
G120X (690V,IP20,18,5kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH30-1UP0	CONVERTER
G120X (690V,IP20,22kW,C2,USS,Blanc,3C2)	6SL3220-1YH32-0AB0	CONVERTER
G120X (690V,IP20,22kW,C2,PN,Blanc,3C2)	6SL3220-1YH32-0AF0	CONVERTER

G120X (690V,IP20,22kW,C2,DP,Blanc,3C2)	6SL3220-1YH32-0AP0	CONVERTER
G120X (690V,IP20,22kW,UF,USS,Blanc,3C2)	6SL3220-1YH32-0UB0	CONVERTER
G120X (690V,IP20,22kW,UF,PN,Blanc,3C2)	6SL3220-1YH32-0UF0	CONVERTER
G120X (690V,IP20,22kW,UF,DP,Blanc,3C2)	6SL3220-1YH32-0UP0	CONVERTER
G120X (690V,IP20,22kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YH32-1AB0	CONVERTER
G120X (690V,IP20,22kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YH32-1AF0	CONVERTER
G120X (690V,IP20,22kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YH32-1AP0	CONVERTER
G120X (690V,IP20,22kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH32-1UB0	CONVERTER
G120X (690V,IP20,22kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH32-1UF0	CONVERTER
G120X (690V,IP20,22kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH32-1UP0	CONVERTER
G120X (690V,IP20,30kW,C2,USS,Blanc,3C2)	6SL3220-1YH34-0AB0	CONVERTER
G120X (690V,IP20,30kW,C2,PN,Blanc,3C2)	6SL3220-1YH34-0AF0	CONVERTER
G120X (690V,IP20,30kW,C2,DP,Blanc,3C2)	6SL3220-1YH34-0AP0	CONVERTER
G120X (690V,IP20,30kW,UF,USS,Blanc,3C2)	6SL3220-1YH34-0UB0	CONVERTER
G120X (690V,IP20,30kW,UF,PN,Blanc,3C2)	6SL3220-1YH34-0UF0	CONVERTER
G120X (690V,IP20,30kW,UF,DP,Blanc,3C2)	6SL3220-1YH34-0UP0	CONVERTER
G120X (690V,IP20,30kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YH34-1AB0	CONVERTER
G120X (690V,IP20,30kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YH34-1AF0	CONVERTER
G120X (690V,IP20,30kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YH34-1AP0	CONVERTER
G120X (690V,IP20,30kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH34-1UB0	CONVERTER
G120X (690V,IP20,30kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH34-1UF0	CONVERTER
G120X (690V,IP20,30kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH34-1UP0	CONVERTER
G120X (690V,IP20,37kW,C2,USS,Blanc,3C2)	6SL3220-1YH36-0AB0	CONVERTER
G120X (690V,IP20,37kW,C2,PN,Blanc,3C2)	6SL3220-1YH36-0AF0	CONVERTER
G120X (690V,IP20,37kW,C2,DP,Blanc,3C2)	6SL3220-1YH36-0AP0	CONVERTER
G120X (690V,IP20,37kW,UF,USS,Blanc,3C2)	6SL3220-1YH36-0UB0	CONVERTER
G120X (690V,IP20,37kW,UF,PN,Blanc,3C2)	6SL3220-1YH36-0UF0	CONVERTER
G120X (690V,IP20,37kW,UF,DP,Blanc,3C2)	6SL3220-1YH36-0UP0	CONVERTER
G120X (690V,IP20,37kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YH36-1AB0	CONVERTER
G120X (690V,IP20,37kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YH36-1AF0	CONVERTER
G120X (690V,IP20,37kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YH36-1AP0	CONVERTER
G120X (690V,IP20,37kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH36-1UB0	CONVERTER
G120X (690V,IP20,37kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH36-1UF0	CONVERTER
G120X (690V,IP20,37kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH36-1UP0	CONVERTER
G120X (690V,IP20,45kW,C2,USS,Blanc,3C2)	6SL3220-1YH38-0AB0	CONVERTER
G120X (690V,IP20,45kW,C2,PN,Blanc,3C2)	6SL3220-1YH38-0AF0	CONVERTER
G120X (690V,IP20,45kW,C2,DP,Blanc,3C2)	6SL3220-1YH38-0AP0	CONVERTER
G120X (690V,IP20,45kW,UF,USS,Blanc,3C2)	6SL3220-1YH38-0UB0	CONVERTER
G120X (690V,IP20,45kW,UF,PN,Blanc,3C2)	6SL3220-1YH38-0UF0	CONVERTER
G120X (690V,IP20,45kW,UF,DP,Blanc,3C2)	6SL3220-1YH38-0UP0	CONVERTER
G120X (690V,IP20,45kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YH38-1AB0	CONVERTER
G120X (690V,IP20,45kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YH38-1AF0	CONVERTER
G120X (690V,IP20,45kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YH38-1AP0	CONVERTER
G120X (690V,IP20,45kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH38-1UB0	CONVERTER

G120X (690V,IP20,45kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH38-1UF0	CONVERTER
G120X (690V,IP20,45kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH38-1UP0	CONVERTER
G120X (690V,IP20,55kW,C2,USS,Blanc,3C2)	6SL3220-1YH40-0AB0	CONVERTER
G120X (690V,IP20,55kW,C2,PN,Blanc,3C2)	6SL3220-1YH40-0AF0	CONVERTER
G120X (690V,IP20,55kW,C2,DP,Blanc,3C2)	6SL3220-1YH40-0AP0	CONVERTER
G120X (690V,IP20,55kW,UF,USS,Blanc,3C2)	6SL3220-1YH40-0UB0	CONVERTER
G120X (690V,IP20,55kW,UF,PN,Blanc,3C2)	6SL3220-1YH40-0UF0	CONVERTER
G120X (690V,IP20,55kW,UF,DP,Blanc,3C2)	6SL3220-1YH40-0UP0	CONVERTER
G120X (690V,IP20,55kW,C2,USS,Blanc,3C2,IO)	6SL3220-1YH40-1AB0	CONVERTER
G120X (690V,IP20,55kW,C2,PN,Blanc,3C2,IO)	6SL3220-1YH40-1AF0	CONVERTER
G120X (690V,IP20,55kW,C2,DP,Blanc,3C2,IO)	6SL3220-1YH40-1AP0	CONVERTER
G120X (690V,IP20,55kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH40-1UB0	CONVERTER
G120X (690V,IP20,55kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH40-1UF0	CONVERTER
G120X (690V,IP20,55kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH40-1UP0	CONVERTER
G120X (690V,IP20,75kW,C3,USS,Blanc,3C2)	6SL3220-1YH42-0CB0	CONVERTER
G120X (690V,IP20,75kW,C3,PN,Blanc,3C2)	6SL3220-1YH42-0CF0	CONVERTER
G120X (690V,IP20,75kW,C3,DP,Blanc,3C2)	6SL3220-1YH42-0CP0	CONVERTER
G120X (690V,IP20,75kW,UF,USS,Blanc,3C2)	6SL3220-1YH42-0UB0	CONVERTER
G120X (690V,IP20,75kW,UF,PN,Blanc,3C2)	6SL3220-1YH42-0UF0	CONVERTER
G120X (690V,IP20,75kW,UF,DP,Blanc,3C2)	6SL3220-1YH42-0UP0	CONVERTER
G120X (690V,IP20,75kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YH42-1CB0	CONVERTER
G120X (690V,IP20,75kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YH42-1CF0	CONVERTER
G120X (690V,IP20,75kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YH42-1CP0	CONVERTER
G120X (690V,IP20,75kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH42-1UB0	CONVERTER
G120X (690V,IP20,75kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH42-1UF0	CONVERTER
G120X (690V,IP20,75kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH42-1UP0	CONVERTER
G120X (690V,IP20,90kW,C3,USS,Blanc,3C2)	6SL3220-1YH44-0CB0	CONVERTER
G120X (690V,IP20,90kW,C3,PN,Blanc,3C2)	6SL3220-1YH44-0CF0	CONVERTER
G120X (690V,IP20,90kW,C3,DP,Blanc,3C2)	6SL3220-1YH44-0CP0	CONVERTER
G120X (690V,IP20,90kW,UF,USS,Blanc,3C2)	6SL3220-1YH44-0UB0	CONVERTER
G120X (690V,IP20,90kW,UF,PN,Blanc,3C2)	6SL3220-1YH44-0UF0	CONVERTER
G120X (690V,IP20,90kW,UF,DP,Blanc,3C2)	6SL3220-1YH44-0UP0	CONVERTER
G120X (690V,IP20,90kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YH44-1CB0	CONVERTER
G120X (690V,IP20,90kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YH44-1CF0	CONVERTER
G120X (690V,IP20,90kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YH44-1CP0	CONVERTER
G120X (690V,IP20,90kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH44-1UB0	CONVERTER
G120X (690V,IP20,90kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH44-1UF0	CONVERTER
G120X (690V,IP20,90kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH44-1UP0	CONVERTER
G120X (690V,IP20,110kW,C3,USS,Blanc,3C2)	6SL3220-1YH46-0CB0	CONVERTER
G120X (690V,IP20,110kW,C3,PN,Blanc,3C2)	6SL3220-1YH46-0CF0	CONVERTER
G120X (690V,IP20,110kW,C3,DP,Blanc,3C2)	6SL3220-1YH46-0CP0	CONVERTER
G120X (690V,IP20,110kW,UF,USS,Blanc,3C2)	6SL3220-1YH46-0UB0	CONVERTER
G120X (690V,IP20,110kW,UF,PN,Blanc,3C2)	6SL3220-1YH46-0UF0	CONVERTER
G120X (690V,IP20,110kW,UF,DP,Blanc,3C2)	6SL3220-1YH46-0UP0	CONVERTER

G120X (690V,IP20,110kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YH46-1CB0	CONVERTER
G120X (690V,IP20,110kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YH46-1CF0	CONVERTER
G120X (690V,IP20,110kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YH46-1CP0	CONVERTER
G120X (690V,IP20,110kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH46-1UB0	CONVERTER
G120X (690V,IP20,110kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH46-1UF0	CONVERTER
G120X (690V,IP20,110kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH46-1UP0	CONVERTER
G120X (690V,IP20,132kW,C3,USS,Blanc,3C2)	6SL3220-1YH48-0CB0	CONVERTER
G120X (690V,IP20,132kW,C3,PN,Blanc,3C2)	6SL3220-1YH48-0CF0	CONVERTER
G120X (690V,IP20,132kW,C3,DP,Blanc,3C2)	6SL3220-1YH48-0CP0	CONVERTER
G120X (690V,IP20,132kW,UF,USS,Blanc,3C2)	6SL3220-1YH48-0UB0	CONVERTER
G120X (690V,IP20,132kW,UF,PN,Blanc,3C2)	6SL3220-1YH48-0UF0	CONVERTER
G120X (690V,IP20,132kW,UF,DP,Blanc,3C2)	6SL3220-1YH48-0UP0	CONVERTER
G120X (690V,IP20,132kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YH48-1CB0	CONVERTER
G120X (690V,IP20,132kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YH48-1CF0	CONVERTER
G120X (690V,IP20,132kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YH48-1CP0	CONVERTER
G120X (690V,IP20,132kW,UF,USS,Blanc,3C2,IO)	6SL3220-1YH48-1UB0	CONVERTER
G120X (690V,IP20,132kW,UF,PN,Blanc,3C2,IO)	6SL3220-1YH48-1UF0	CONVERTER
G120X (690V,IP20,132kW,UF,DP,Blanc,3C2,IO)	6SL3220-1YH48-1UP0	CONVERTER
G120X (690V,IP20,160kW,C3,USS,Blanc,3C2)	6SL3220-1YH50-0CB0	CONVERTER
G120X (690V,IP20,160kW,C3,PN,Blanc,3C2)	6SL3220-1YH50-0CF0	CONVERTER
G120X (690V,IP20,160kW,C3,DP,Blanc,3C2)	6SL3220-1YH50-0CP0	CONVERTER
G120X (690V,IP20,160kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YH50-1CB0	CONVERTER
G120X (690V,IP20,160kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YH50-1CF0	CONVERTER
G120X (690V,IP20,160kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YH50-1CP0	CONVERTER
G120X (690V,IP20,200kW,C3,USS,Blanc,3C2)	6SL3220-1YH52-0CB0	CONVERTER
G120X (690V,IP20,200kW,C3,PN,Blanc,3C2)	6SL3220-1YH52-0CF0	CONVERTER
G120X (690V,IP20,200kW,C3,DP,Blanc,3C2)	6SL3220-1YH52-0CP0	CONVERTER
G120X (690V,IP20,200kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YH52-1CB0	CONVERTER
G120X (690V,IP20,200kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YH52-1CF0	CONVERTER
G120X (690V,IP20,200kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YH52-1CP0	CONVERTER
G120X (690V,IP20,250kW,C3,USS,Blanc,3C2)	6SL3220-1YH54-0CB0	CONVERTER
G120X (690V,IP20,250kW,C3,PN,Blanc,3C2)	6SL3220-1YH54-0CF0	CONVERTER
G120X (690V,IP20,250kW,C3,DP,Blanc,3C2)	6SL3220-1YH54-0CP0	CONVERTER
G120X (690V,IP20,250kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YH54-1CB0	CONVERTER
G120X (690V,IP20,250kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YH54-1CF0	CONVERTER
G120X (690V,IP20,250kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YH54-1CP0	CONVERTER
G120X (690V,IP20,315kW,C3,USS,Blanc,3C2)	6SL3220-1YH56-0CB0	CONVERTER
G120X (690V,IP20,315kW,C3,PN,Blanc,3C2)	6SL3220-1YH56-0CF0	CONVERTER
G120X (690V,IP20,315kW,C3,DP,Blanc,3C2)	6SL3220-1YH56-0CP0	CONVERTER
G120X (690V,IP20,315kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YH56-1CB0	CONVERTER
G120X (690V,IP20,315kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YH56-1CF0	CONVERTER
G120X (690V,IP20,315kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YH56-1CP0	CONVERTER
G120X (690V,IP20,355kW,C3,USS,Blanc,3C2)	6SL3220-1YH58-0CB0	CONVERTER
G120X (690V,IP20,355kW,C3,PN,Blanc,3C2)	6SL3220-1YH58-0CF0	CONVERTER

G120X (690V,IP20,355kW,C3,DP,Blanc,3C2)	6SL3220-1YH58-0CP0	CONVERTER
G120X (690V,IP20,355kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YH58-1CB0	CONVERTER
G120X (690V,IP20,355kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YH58-1CF0	CONVERTER
G120X (690V,IP20,355kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YH58-1CP0	CONVERTER
G120X (690V,IP20,400kW,C3,USS,Blanc,3C2)	6SL3220-1YH60-0CB0	CONVERTER
G120X (690V,IP20,400kW,C3,PN,Blanc,3C2)	6SL3220-1YH60-0CF0	CONVERTER
G120X (690V,IP20,400kW,C3,DP,Blanc,3C2)	6SL3220-1YH60-0CP0	CONVERTER
G120X (690V,IP20,400kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YH60-1CB0	CONVERTER
G120X (690V,IP20,400kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YH60-1CF0	CONVERTER
G120X (690V,IP20,400kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YH60-1CP0	CONVERTER
G120X (690V,IP20,450kW,C3,USS,Blanc,3C2)	6SL3220-1YH62-0CB0	CONVERTER
G120X (690V,IP20,450kW,C3,PN,Blanc,3C2)	6SL3220-1YH62-0CF0	CONVERTER
G120X (690V,IP20,450kW,C3,DP,Blanc,3C2)	6SL3220-1YH62-0CP0	CONVERTER
G120X (690V,IP20,450kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YH62-1CB0	CONVERTER
G120X (690V,IP20,450kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YH62-1CF0	CONVERTER
G120X (690V,IP20,450kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YH62-1CP0	CONVERTER
G120X (690V,IP20,500kW,C3,USS,Blanc,3C2)	6SL3220-1YH64-0CB0	CONVERTER
G120X (690V,IP20,500kW,C3,PN,Blanc,3C2)	6SL3220-1YH64-0CF0	CONVERTER
G120X (690V,IP20,500kW,C3,DP,Blanc,3C2)	6SL3220-1YH64-0CP0	CONVERTER
G120X (690V,IP20,500kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YH64-1CB0	CONVERTER
G120X (690V,IP20,500kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YH64-1CF0	CONVERTER
G120X (690V,IP20,500kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YH64-1CP0	CONVERTER
G120X (690V,IP20,560kW,C3,USS,Blanc,3C2)	6SL3220-1YH66-0CB0	CONVERTER
G120X (690V,IP20,560kW,C3,PN,Blanc,3C2)	6SL3220-1YH66-0CF0	CONVERTER
G120X (690V,IP20,560kW,C3,DP,Blanc,3C2)	6SL3220-1YH66-0CP0	CONVERTER
G120X (690V,IP20,560kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YH66-1CB0	CONVERTER
G120X (690V,IP20,560kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YH66-1CF0	CONVERTER
G120X (690V,IP20,560kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YH66-1CP0	CONVERTER
G120X (690V,IP20,630kW,C3,USS,Blanc,3C2)	6SL3220-1YH68-0CB0	CONVERTER
G120X (690V,IP20,630kW,C3,PN,Blanc,3C2)	6SL3220-1YH68-0CF0	CONVERTER
G120X (690V,IP20,630kW,C3,DP,Blanc,3C2)	6SL3220-1YH68-0CP0	CONVERTER
G120X (690V,IP20,630kW,C3,USS,Blanc,3C2,IO)	6SL3220-1YH68-1CB0	CONVERTER
G120X (690V,IP20,630kW,C3,PN,Blanc,3C2,IO)	6SL3220-1YH68-1CF0	CONVERTER
G120X (690V,IP20,630kW,C3,DP,Blanc,3C2,IO)	6SL3220-1YH68-1CP0	CONVERTER
G120X (230V,IP20,0.75kW,UF,USS,BOP-2,3C2)	6SL3220-2YC10-0UB0	CONVERTER
G120X (230V,IP20,0.75kW,UF,PN,BOP-2,3C2)	6SL3220-2YC10-0UF0	CONVERTER
G120X (230V,IP20,0.75kW,UF,DP,BOP-2,3C2)	6SL3220-2YC10-0UP0	CONVERTER
G120X (230V,IP20,0.75kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC10-1UB0	CONVERTER
G120X (230V,IP20,0.75kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC10-1UF0	CONVERTER
G120X (230V,IP20,0.75kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC10-1UP0	CONVERTER
G120X (230V,IP20,1.1kW,UF,USS,BOP-2,3C2)	6SL3220-2YC12-0UB0	CONVERTER
G120X (230V,IP20,1.1kW,UF,PN,BOP-2,3C2)	6SL3220-2YC12-0UF0	CONVERTER
G120X (230V,IP20,1.1kW,UF,DP,BOP-2,3C2)	6SL3220-2YC12-0UP0	CONVERTER
G120X (230V,IP20,1.1kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC12-1UB0	CONVERTER

G120X (230V,IP20,1.1kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC12-1UF0	CONVERTER
G120X (230V,IP20,1.1kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC12-1UP0	CONVERTER
G120X (230V,IP20,1.5kW,UF,USS,BOP-2,3C2)	6SL3220-2YC14-0UB0	CONVERTER
G120X (230V,IP20,1.5kW,UF,PN,BOP-2,3C2)	6SL3220-2YC14-0UF0	CONVERTER
G120X (230V,IP20,1.5kW,UF,DP,BOP-2,3C2)	6SL3220-2YC14-0UP0	CONVERTER
G120X (230V,IP20,1.5kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC14-1UB0	CONVERTER
G120X (230V,IP20,1.5kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC14-1UF0	CONVERTER
G120X (230V,IP20,1.5kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC14-1UP0	CONVERTER
G120X (230V,IP20,2.2kW,UF,USS,BOP-2,3C2)	6SL3220-2YC16-0UB0	CONVERTER
G120X (230V,IP20,2.2kW,UF,PN,BOP-2,3C2)	6SL3220-2YC16-0UF0	CONVERTER
G120X (230V,IP20,2.2kW,UF,DP,BOP-2,3C2)	6SL3220-2YC16-0UP0	CONVERTER
G120X (230V,IP20,2.2kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC16-1UB0	CONVERTER
G120X (230V,IP20,2.2kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC16-1UF0	CONVERTER
G120X (230V,IP20,2.2kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC16-1UP0	CONVERTER
G120X (230V,IP20,3kW,UF,USS,BOP-2,3C2)	6SL3220-2YC18-0UB0	CONVERTER
G120X (230V,IP20,3kW,UF,PN,BOP-2,3C2)	6SL3220-2YC18-0UF0	CONVERTER
G120X (230V,IP20,3kW,UF,DP,BOP-2,3C2)	6SL3220-2YC18-0UP0	CONVERTER
G120X (230V,IP20,3kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC18-1UB0	CONVERTER
G120X (230V,IP20,3kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC18-1UF0	CONVERTER
G120X (230V,IP20,3kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC18-1UP0	CONVERTER
G120X (230V,IP20,4kW,UF,USS,BOP-2,3C2)	6SL3220-2YC20-0UB0	CONVERTER
G120X (230V,IP20,4kW,UF,PN,BOP-2,3C2)	6SL3220-2YC20-0UF0	CONVERTER
G120X (230V,IP20,4kW,UF,DP,BOP-2,3C2)	6SL3220-2YC20-0UP0	CONVERTER
G120X (230V,IP20,4kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC20-1UB0	CONVERTER
G120X (230V,IP20,4kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC20-1UF0	CONVERTER
G120X (230V,IP20,4kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC20-1UP0	CONVERTER
G120X (230V,IP20,5.5kW,UF,USS,BOP-2,3C2)	6SL3220-2YC22-0UB0	CONVERTER
G120X (230V,IP20,5.5kW,UF,PN,BOP-2,3C2)	6SL3220-2YC22-0UF0	CONVERTER
G120X (230V,IP20,5.5kW,UF,DP,BOP-2,3C2)	6SL3220-2YC22-0UP0	CONVERTER
G120X (230V,IP20,5.5kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC22-1UB0	CONVERTER
G120X (230V,IP20,5.5kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC22-1UF0	CONVERTER
G120X (230V,IP20,5.5kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC22-1UP0	CONVERTER
G120X (230V,IP20,7.5kW,UF,USS,BOP-2,3C2)	6SL3220-2YC24-0UB0	CONVERTER
G120X (230V,IP20,7.5kW,UF,PN,BOP-2,3C2)	6SL3220-2YC24-0UF0	CONVERTER
G120X (230V,IP20,7.5kW,UF,DP,BOP-2,3C2)	6SL3220-2YC24-0UP0	CONVERTER
G120X (230V,IP20,7.5kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC24-1UB0	CONVERTER
G120X (230V,IP20,7.5kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC24-1UF0	CONVERTER
G120X (230V,IP20,7.5kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC24-1UP0	CONVERTER
G120X (230V,IP20,11kW,UF,USS,BOP-2,3C2)	6SL3220-2YC26-0UB0	CONVERTER
G120X (230V,IP20,11kW,UF,PN,BOP-2,3C2)	6SL3220-2YC26-0UF0	CONVERTER
G120X (230V,IP20,11kW,UF,DP,BOP-2,3C2)	6SL3220-2YC26-0UP0	CONVERTER
G120X (230V,IP20,11kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC26-1UB0	CONVERTER
G120X (230V,IP20,11kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC26-1UF0	CONVERTER
G120X (230V,IP20,11kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC26-1UP0	CONVERTER

G120X (230V,IP20,15kW,UF,USS,BOP-2,3C2)	6SL3220-2YC28-0UB0	CONVERTER
G120X (230V,IP20,15kW,UF,PN,BOP-2,3C2)	6SL3220-2YC28-0UF0	CONVERTER
G120X (230V,IP20,15kW,UF,DP,BOP-2,3C2)	6SL3220-2YC28-0UP0	CONVERTER
G120X (230V,IP20,15kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC28-1UB0	CONVERTER
G120X (230V,IP20,15kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC28-1UF0	CONVERTER
G120X (230V,IP20,15kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC28-1UP0	CONVERTER
G120X (230V,IP20,18,5kW,UF,USS,BOP-2,3C2)	6SL3220-2YC30-0UB0	CONVERTER
G120X (230V,IP20,18,5kW,UF,PN,BOP-2,3C2)	6SL3220-2YC30-0UF0	CONVERTER
G120X (230V,IP20,18,5kW,UF,DP,BOP-2,3C2)	6SL3220-2YC30-0UP0	CONVERTER
G120X (230V,IP20,18,5kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC30-1UB0	CONVERTER
G120X (230V,IP20,18,5kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC30-1UF0	CONVERTER
G120X (230V,IP20,18,5kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC30-1UP0	CONVERTER
G120X (230V,IP20,22kW,UF,USS,BOP-2,3C2)	6SL3220-2YC32-0UB0	CONVERTER
G120X (230V,IP20,22kW,UF,PN,BOP-2,3C2)	6SL3220-2YC32-0UF0	CONVERTER
G120X (230V,IP20,22kW,UF,DP,BOP-2,3C2)	6SL3220-2YC32-0UP0	CONVERTER
G120X (230V,IP20,22kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC32-1UB0	CONVERTER
G120X (230V,IP20,22kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC32-1UF0	CONVERTER
G120X (230V,IP20,22kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC32-1UP0	CONVERTER
G120X (230V,IP20,30kW,UF,USS,BOP-2,3C2)	6SL3220-2YC34-0UB0	CONVERTER
G120X (230V,IP20,30kW,UF,PN,BOP-2,3C2)	6SL3220-2YC34-0UF0	CONVERTER
G120X (230V,IP20,30kW,UF,DP,BOP-2,3C2)	6SL3220-2YC34-0UP0	CONVERTER
G120X (230V,IP20,30kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC34-1UB0	CONVERTER
G120X (230V,IP20,30kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC34-1UF0	CONVERTER
G120X (230V,IP20,30kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC34-1UP0	CONVERTER
G120X (230V,IP20,37kW,UF,USS,BOP-2,3C2)	6SL3220-2YC36-0UB0	CONVERTER
G120X (230V,IP20,37kW,UF,PN,BOP-2,3C2)	6SL3220-2YC36-0UF0	CONVERTER
G120X (230V,IP20,37kW,UF,DP,BOP-2,3C2)	6SL3220-2YC36-0UP0	CONVERTER
G120X (230V,IP20,37kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC36-1UB0	CONVERTER
G120X (230V,IP20,37kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC36-1UF0	CONVERTER
G120X (230V,IP20,37kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC36-1UP0	CONVERTER
G120X (230V,IP20,45kW,UF,USS,BOP-2,3C2)	6SL3220-2YC38-0UB0	CONVERTER
G120X (230V,IP20,45kW,UF,PN,BOP-2,3C2)	6SL3220-2YC38-0UF0	CONVERTER
G120X (230V,IP20,45kW,UF,DP,BOP-2,3C2)	6SL3220-2YC38-0UP0	CONVERTER
G120X (230V,IP20,45kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC38-1UB0	CONVERTER
G120X (230V,IP20,45kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC38-1UF0	CONVERTER
G120X (230V,IP20,45kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC38-1UP0	CONVERTER
G120X (230V,IP20,55kW,UF,USS,BOP-2,3C2)	6SL3220-2YC40-0UB0	CONVERTER
G120X (230V,IP20,55kW,UF,PN,BOP-2,3C2)	6SL3220-2YC40-0UF0	CONVERTER
G120X (230V,IP20,55kW,UF,DP,BOP-2,3C2)	6SL3220-2YC40-0UP0	CONVERTER
G120X (230V,IP20,55kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YC40-1UB0	CONVERTER
G120X (230V,IP20,55kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YC40-1UF0	CONVERTER
G120X (230V,IP20,55kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YC40-1UP0	CONVERTER
G120X (400V,IP20,0.75kW,C2,USS,BOP-2,3C2)	6SL3220-2YE10-0AB0	CONVERTER
G120X (400V,IP20,0.75kW,C2,PN,BOP-2,3C2)	6SL3220-2YE10-0AF0	CONVERTER

G120X (400V,IP20,0.75kW,C2,DP,BOP-2,3C2)	6SL3220-2YE10-0AP0	CONVERTER
G120X (400V,IP20,0.75kW,UF,USS,BOP-2,3C2)	6SL3220-2YE10-0UB0	CONVERTER
G120X (400V,IP20,0.75kW,UF,PN,BOP-2,3C2)	6SL3220-2YE10-0UF0	CONVERTER
G120X (400V,IP20,0.75kW,UF,DP,BOP-2,3C2)	6SL3220-2YE10-0UP0	CONVERTER
G120X (400V,IP20,0.75kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE10-1AB0	CONVERTER
G120X (400V,IP20,0.75kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE10-1AF0	CONVERTER
G120X (400V,IP20,0.75kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE10-1AP0	CONVERTER
G120X (400V,IP20,0.75kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE10-1UB0	CONVERTER
G120X (400V,IP20,0.75kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE10-1UF0	CONVERTER
G120X (400V,IP20,0.75kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE10-1UP0	CONVERTER
G120X (400V,IP20,1.1kW,C2,USS,BOP-2,3C2)	6SL3220-2YE12-0AB0	CONVERTER
G120X (400V,IP20,1.1kW,C2,PN,BOP-2,3C2)	6SL3220-2YE12-0AF0	CONVERTER
G120X (400V,IP20,1.1kW,C2,DP,BOP-2,3C2)	6SL3220-2YE12-0AP0	CONVERTER
G120X (400V,IP20,1.1kW,UF,USS,BOP-2,3C2)	6SL3220-2YE12-0UB0	CONVERTER
G120X (400V,IP20,1.1kW,UF,PN,BOP-2,3C2)	6SL3220-2YE12-0UF0	CONVERTER
G120X (400V,IP20,1.1kW,UF,DP,BOP-2,3C2)	6SL3220-2YE12-0UP0	CONVERTER
G120X (400V,IP20,1.1kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE12-1AB0	CONVERTER
G120X (400V,IP20,1.1kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE12-1AF0	CONVERTER
G120X (400V,IP20,1.1kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE12-1AP0	CONVERTER
G120X (400V,IP20,1.1kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE12-1UB0	CONVERTER
G120X (400V,IP20,1.1kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE12-1UF0	CONVERTER
G120X (400V,IP20,1.1kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE12-1UP0	CONVERTER
G120X (400V,IP20,1.5kW,C2,USS,BOP-2,3C2)	6SL3220-2YE14-0AB0	CONVERTER
G120X (400V,IP20,1.5kW,C2,PN,BOP-2,3C2)	6SL3220-2YE14-0AF0	CONVERTER
G120X (400V,IP20,1.5kW,C2,DP,BOP-2,3C2)	6SL3220-2YE14-0AP0	CONVERTER
G120X (400V,IP20,1.5kW,UF,USS,BOP-2,3C2)	6SL3220-2YE14-0UB0	CONVERTER
G120X (400V,IP20,1.5kW,UF,PN,BOP-2,3C2)	6SL3220-2YE14-0UF0	CONVERTER
G120X (400V,IP20,1.5kW,UF,DP,BOP-2,3C2)	6SL3220-2YE14-0UP0	CONVERTER
G120X (400V,IP20,1.5kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE14-1AB0	CONVERTER
G120X (400V,IP20,1.5kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE14-1AF0	CONVERTER
G120X (400V,IP20,1.5kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE14-1AP0	CONVERTER
G120X (400V,IP20,1.5kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE14-1UB0	CONVERTER
G120X (400V,IP20,1.5kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE14-1UF0	CONVERTER
G120X (400V,IP20,1.5kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE14-1UP0	CONVERTER
G120X (400V,IP20,2.2kW,C2,USS,BOP-2,3C2)	6SL3220-2YE16-0AB0	CONVERTER
G120X (400V,IP20,2.2kW,C2,PN,BOP-2,3C2)	6SL3220-2YE16-0AF0	CONVERTER
G120X (400V,IP20,2.2kW,C2,DP,BOP-2,3C2)	6SL3220-2YE16-0AP0	CONVERTER
G120X (400V,IP20,2.2kW,UF,USS,BOP-2,3C2)	6SL3220-2YE16-0UB0	CONVERTER
G120X (400V,IP20,2.2kW,UF,PN,BOP-2,3C2)	6SL3220-2YE16-0UF0	CONVERTER
G120X (400V,IP20,2.2kW,UF,DP,BOP-2,3C2)	6SL3220-2YE16-0UP0	CONVERTER
G120X (400V,IP20,2.2kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE16-1AB0	CONVERTER
G120X (400V,IP20,2.2kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE16-1AF0	CONVERTER
G120X (400V,IP20,2.2kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE16-1AP0	CONVERTER
G120X (400V,IP20,2.2kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE16-1UB0	CONVERTER

G120X (400V,IP20,2.2kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE16-1UF0	CONVERTER
G120X (400V,IP20,2.2kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE16-1UP0	CONVERTER
G120X (400V,IP20,3kW,C2,USS,BOP-2,3C2)	6SL3220-2YE18-0AB0	CONVERTER
G120X (400V,IP20,3kW,C2,PN,BOP-2,3C2)	6SL3220-2YE18-0AF0	CONVERTER
G120X (400V,IP20,3kW,C2,DP,BOP-2,3C2)	6SL3220-2YE18-0AP0	CONVERTER
G120X (400V,IP20,3kW,UF,USS,BOP-2,3C2)	6SL3220-2YE18-0UB0	CONVERTER
G120X (400V,IP20,3kW,UF,PN,BOP-2,3C2)	6SL3220-2YE18-0UF0	CONVERTER
G120X (400V,IP20,3kW,UF,DP,BOP-2,3C2)	6SL3220-2YE18-0UP0	CONVERTER
G120X (400V,IP20,3kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE18-1AB0	CONVERTER
G120X (400V,IP20,3kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE18-1AF0	CONVERTER
G120X (400V,IP20,3kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE18-1AP0	CONVERTER
G120X (400V,IP20,3kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE18-1UB0	CONVERTER
G120X (400V,IP20,3kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE18-1UF0	CONVERTER
G120X (400V,IP20,3kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE18-1UP0	CONVERTER
G120X (400V,IP20,4kW,C2,USS,BOP-2,3C2)	6SL3220-2YE20-0AB0	CONVERTER
G120X (400V,IP20,4kW,C2,PN,BOP-2,3C2)	6SL3220-2YE20-0AF0	CONVERTER
G120X (400V,IP20,4kW,C2,DP,BOP-2,3C2)	6SL3220-2YE20-0AP0	CONVERTER
G120X (400V,IP20,4kW,UF,USS,BOP-2,3C2)	6SL3220-2YE20-0UB0	CONVERTER
G120X (400V,IP20,4kW,UF,PN,BOP-2,3C2)	6SL3220-2YE20-0UF0	CONVERTER
G120X (400V,IP20,4kW,UF,DP,BOP-2,3C2)	6SL3220-2YE20-0UP0	CONVERTER
G120X (400V,IP20,4kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE20-1AB0	CONVERTER
G120X (400V,IP20,4kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE20-1AF0	CONVERTER
G120X (400V,IP20,4kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE20-1AP0	CONVERTER
G120X (400V,IP20,4kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE20-1UB0	CONVERTER
G120X (400V,IP20,4kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE20-1UF0	CONVERTER
G120X (400V,IP20,4kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE20-1UP0	CONVERTER
G120X (400V,IP20,5.5kW,C2,USS,BOP-2,3C2)	6SL3220-2YE22-0AB0	CONVERTER
G120X (400V,IP20,5.5kW,C2,PN,BOP-2,3C2)	6SL3220-2YE22-0AF0	CONVERTER
G120X (400V,IP20,5.5kW,C2,DP,BOP-2,3C2)	6SL3220-2YE22-0AP0	CONVERTER
G120X (400V,IP20,5.5kW,UF,USS,BOP-2,3C2)	6SL3220-2YE22-0UB0	CONVERTER
G120X (400V,IP20,5.5kW,UF,PN,BOP-2,3C2)	6SL3220-2YE22-0UF0	CONVERTER
G120X (400V,IP20,5.5kW,UF,DP,BOP-2,3C2)	6SL3220-2YE22-0UP0	CONVERTER
G120X (400V,IP20,5.5kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE22-1AB0	CONVERTER
G120X (400V,IP20,5.5kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE22-1AF0	CONVERTER
G120X (400V,IP20,5.5kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE22-1AP0	CONVERTER
G120X (400V,IP20,5.5kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE22-1UB0	CONVERTER
G120X (400V,IP20,5.5kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE22-1UF0	CONVERTER
G120X (400V,IP20,5.5kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE22-1UP0	CONVERTER
G120X (400V,IP20,7.5kW,C2,USS,BOP-2,3C2)	6SL3220-2YE24-0AB0	CONVERTER
G120X (400V,IP20,7.5kW,C2,PN,BOP-2,3C2)	6SL3220-2YE24-0AF0	CONVERTER
G120X (400V,IP20,7.5kW,C2,DP,BOP-2,3C2)	6SL3220-2YE24-0AP0	CONVERTER
G120X (400V,IP20,7.5kW,UF,USS,BOP-2,3C2)	6SL3220-2YE24-0UB0	CONVERTER
G120X (400V,IP20,7.5kW,UF,PN,BOP-2,3C2)	6SL3220-2YE24-0UF0	CONVERTER
G120X (400V,IP20,7.5kW,UF,DP,BOP-2,3C2)	6SL3220-2YE24-0UP0	CONVERTER

G120X (400V,IP20,7.5kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE24-1AB0	CONVERTER
G120X (400V,IP20,7.5kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE24-1AF0	CONVERTER
G120X (400V,IP20,7.5kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE24-1AP0	CONVERTER
G120X (400V,IP20,7.5kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE24-1UB0	CONVERTER
G120X (400V,IP20,7.5kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE24-1UF0	CONVERTER
G120X (400V,IP20,7.5kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE24-1UP0	CONVERTER
G120X (400V,IP20,11kW,C2,USS,BOP-2,3C2)	6SL3220-2YE26-0AB0	CONVERTER
G120X (400V,IP20,11kW,C2,PN,BOP-2,3C2)	6SL3220-2YE26-0AF0	CONVERTER
G120X (400V,IP20,11kW,C2,DP,BOP-2,3C2)	6SL3220-2YE26-0AP0	CONVERTER
G120X (400V,IP20,11kW,UF,USS,BOP-2,3C2)	6SL3220-2YE26-0UB0	CONVERTER
G120X (400V,IP20,11kW,UF,PN,BOP-2,3C2)	6SL3220-2YE26-0UF0	CONVERTER
G120X (400V,IP20,11kW,UF,DP,BOP-2,3C2)	6SL3220-2YE26-0UP0	CONVERTER
G120X (400V,IP20,11kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE26-1AB0	CONVERTER
G120X (400V,IP20,11kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE26-1AF0	CONVERTER
G120X (400V,IP20,11kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE26-1AP0	CONVERTER
G120X (400V,IP20,11kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE26-1UB0	CONVERTER
G120X (400V,IP20,11kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE26-1UF0	CONVERTER
G120X (400V,IP20,11kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE26-1UP0	CONVERTER
G120X (400V,IP20,15kW,C2,USS,BOP-2,3C2)	6SL3220-2YE28-0AB0	CONVERTER
G120X (400V,IP20,15kW,C2,PN,BOP-2,3C2)	6SL3220-2YE28-0AF0	CONVERTER
G120X (400V,IP20,15kW,C2,DP,BOP-2,3C2)	6SL3220-2YE28-0AP0	CONVERTER
G120X (400V,IP20,15kW,UF,USS,BOP-2,3C2)	6SL3220-2YE28-0UB0	CONVERTER
G120X (400V,IP20,15kW,UF,PN,BOP-2,3C2)	6SL3220-2YE28-0UF0	CONVERTER
G120X (400V,IP20,15kW,UF,DP,BOP-2,3C2)	6SL3220-2YE28-0UP0	CONVERTER
G120X (400V,IP20,15kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE28-1AB0	CONVERTER
G120X (400V,IP20,15kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE28-1AF0	CONVERTER
G120X (400V,IP20,15kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE28-1AP0	CONVERTER
G120X (400V,IP20,15kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE28-1UB0	CONVERTER
G120X (400V,IP20,15kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE28-1UF0	CONVERTER
G120X (400V,IP20,15kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE28-1UP0	CONVERTER
G120X (400V,IP20,18,5kW,C2,USS,BOP-2,3C2)	6SL3220-2YE30-0AB0	CONVERTER
G120X (400V,IP20,18,5kW,C2,PN,BOP-2,3C2)	6SL3220-2YE30-0AF0	CONVERTER
G120X (400V,IP20,18,5kW,C2,DP,BOP-2,3C2)	6SL3220-2YE30-0AP0	CONVERTER
G120X (400V,IP20,18,5kW,UF,USS,BOP-2,3C2)	6SL3220-2YE30-0UB0	CONVERTER
G120X (400V,IP20,18,5kW,UF,PN,BOP-2,3C2)	6SL3220-2YE30-0UF0	CONVERTER
G120X (400V,IP20,18,5kW,UF,DP,BOP-2,3C2)	6SL3220-2YE30-0UP0	CONVERTER
G120X (400V,IP20,18,5kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE30-1AB0	CONVERTER
G120X (400V,IP20,18,5kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE30-1AF0	CONVERTER
G120X (400V,IP20,18,5kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE30-1AP0	CONVERTER
G120X (400V,IP20,18,5kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE30-1UB0	CONVERTER
G120X (400V,IP20,18,5kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE30-1UF0	CONVERTER
G120X (400V,IP20,18,5kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE30-1UP0	CONVERTER
G120X (400V,IP20,22kW,C2,USS,BOP-2,3C2)	6SL3220-2YE32-0AB0	CONVERTER
G120X (400V,IP20,22kW,C2,PN,BOP-2,3C2)	6SL3220-2YE32-0AF0	CONVERTER

G120X (400V,IP20,22kW,C2,DP,BOP-2,3C2)	6SL3220-2YE32-0AP0	CONVERTER
G120X (400V,IP20,22kW,UF,USS,BOP-2,3C2)	6SL3220-2YE32-0UB0	CONVERTER
G120X (400V,IP20,22kW,UF,PN,BOP-2,3C2)	6SL3220-2YE32-0UF0	CONVERTER
G120X (400V,IP20,22kW,UF,DP,BOP-2,3C2)	6SL3220-2YE32-0UP0	CONVERTER
G120X (400V,IP20,22kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE32-1AB0	CONVERTER
G120X (400V,IP20,22kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE32-1AF0	CONVERTER
G120X (400V,IP20,22kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE32-1AP0	CONVERTER
G120X (400V,IP20,22kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE32-1UB0	CONVERTER
G120X (400V,IP20,22kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE32-1UF0	CONVERTER
G120X (400V,IP20,22kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE32-1UP0	CONVERTER
G120X (400V,IP20,30kW,C2,USS,BOP-2,3C2)	6SL3220-2YE34-0AB0	CONVERTER
G120X (400V,IP20,30kW,C2,PN,BOP-2,3C2)	6SL3220-2YE34-0AF0	CONVERTER
G120X (400V,IP20,30kW,C2,DP,BOP-2,3C2)	6SL3220-2YE34-0AP0	CONVERTER
G120X (400V,IP20,30kW,UF,USS,BOP-2,3C2)	6SL3220-2YE34-0UB0	CONVERTER
G120X (400V,IP20,30kW,UF,PN,BOP-2,3C2)	6SL3220-2YE34-0UF0	CONVERTER
G120X (400V,IP20,30kW,UF,DP,BOP-2,3C2)	6SL3220-2YE34-0UP0	CONVERTER
G120X (400V,IP20,30kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE34-1AB0	CONVERTER
G120X (400V,IP20,30kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE34-1AF0	CONVERTER
G120X (400V,IP20,30kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE34-1AP0	CONVERTER
G120X (400V,IP20,30kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE34-1UB0	CONVERTER
G120X (400V,IP20,30kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE34-1UF0	CONVERTER
G120X (400V,IP20,30kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE34-1UP0	CONVERTER
G120X (400V,IP20,37kW,C2,USS,BOP-2,3C2)	6SL3220-2YE36-0AB0	CONVERTER
G120X (400V,IP20,37kW,C2,PN,BOP-2,3C2)	6SL3220-2YE36-0AF0	CONVERTER
G120X (400V,IP20,37kW,C2,DP,BOP-2,3C2)	6SL3220-2YE36-0AP0	CONVERTER
G120X (400V,IP20,37kW,UF,USS,BOP-2,3C2)	6SL3220-2YE36-0UB0	CONVERTER
G120X (400V,IP20,37kW,UF,PN,BOP-2,3C2)	6SL3220-2YE36-0UF0	CONVERTER
G120X (400V,IP20,37kW,UF,DP,BOP-2,3C2)	6SL3220-2YE36-0UP0	CONVERTER
G120X (400V,IP20,37kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE36-1AB0	CONVERTER
G120X (400V,IP20,37kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE36-1AF0	CONVERTER
G120X (400V,IP20,37kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE36-1AP0	CONVERTER
G120X (400V,IP20,37kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE36-1UB0	CONVERTER
G120X (400V,IP20,37kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE36-1UF0	CONVERTER
G120X (400V,IP20,37kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE36-1UP0	CONVERTER
G120X (400V,IP20,45kW,C2,USS,BOP-2,3C2)	6SL3220-2YE38-0AB0	CONVERTER
G120X (400V,IP20,45kW,C2,PN,BOP-2,3C2)	6SL3220-2YE38-0AF0	CONVERTER
G120X (400V,IP20,45kW,C2,DP,BOP-2,3C2)	6SL3220-2YE38-0AP0	CONVERTER
G120X (400V,IP20,45kW,UF,USS,BOP-2,3C2)	6SL3220-2YE38-0UB0	CONVERTER
G120X (400V,IP20,45kW,UF,PN,BOP-2,3C2)	6SL3220-2YE38-0UF0	CONVERTER
G120X (400V,IP20,45kW,UF,DP,BOP-2,3C2)	6SL3220-2YE38-0UP0	CONVERTER
G120X (400V,IP20,45kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE38-1AB0	CONVERTER
G120X (400V,IP20,45kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE38-1AF0	CONVERTER
G120X (400V,IP20,45kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE38-1AP0	CONVERTER
G120X (400V,IP20,45kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE38-1UB0	CONVERTER

G120X (400V,IP20,45kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE38-1UF0	CONVERTER
G120X (400V,IP20,45kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE38-1UP0	CONVERTER
G120X (400V,IP20,55kW,C2,USS,BOP-2,3C2)	6SL3220-2YE40-0AB0	CONVERTER
G120X (400V,IP20,55kW,C2,PN,BOP-2,3C2)	6SL3220-2YE40-0AF0	CONVERTER
G120X (400V,IP20,55kW,C2,DP,BOP-2,3C2)	6SL3220-2YE40-0AP0	CONVERTER
G120X (400V,IP20,55kW,UF,USS,BOP-2,3C2)	6SL3220-2YE40-0UB0	CONVERTER
G120X (400V,IP20,55kW,UF,PN,BOP-2,3C2)	6SL3220-2YE40-0UF0	CONVERTER
G120X (400V,IP20,55kW,UF,DP,BOP-2,3C2)	6SL3220-2YE40-0UP0	CONVERTER
G120X (400V,IP20,55kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE40-1AB0	CONVERTER
G120X (400V,IP20,55kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE40-1AF0	CONVERTER
G120X (400V,IP20,55kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE40-1AP0	CONVERTER
G120X (400V,IP20,55kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE40-1UB0	CONVERTER
G120X (400V,IP20,55kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE40-1UF0	CONVERTER
G120X (400V,IP20,55kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE40-1UP0	CONVERTER
G120X (400V,IP20,75kW,C2,USS,BOP-2,3C2)	6SL3220-2YE42-0AB0	CONVERTER
G120X (400V,IP20,75kW,C2,PN,BOP-2,3C2)	6SL3220-2YE42-0AF0	CONVERTER
G120X (400V,IP20,75kW,C2,DP,BOP-2,3C2)	6SL3220-2YE42-0AP0	CONVERTER
G120X (400V,IP20,75kW,UF,USS,BOP-2,3C2)	6SL3220-2YE42-0UB0	CONVERTER
G120X (400V,IP20,75kW,UF,PN,BOP-2,3C2)	6SL3220-2YE42-0UF0	CONVERTER
G120X (400V,IP20,75kW,UF,DP,BOP-2,3C2)	6SL3220-2YE42-0UP0	CONVERTER
G120X (400V,IP20,75kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE42-1AB0	CONVERTER
G120X (400V,IP20,75kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE42-1AF0	CONVERTER
G120X (400V,IP20,75kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE42-1AP0	CONVERTER
G120X (400V,IP20,75kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE42-1UB0	CONVERTER
G120X (400V,IP20,75kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE42-1UF0	CONVERTER
G120X (400V,IP20,75kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE42-1UP0	CONVERTER
G120X (400V,IP20,90kW,C2,USS,BOP-2,3C2)	6SL3220-2YE44-0AB0	CONVERTER
G120X (400V,IP20,90kW,C2,PN,BOP-2,3C2)	6SL3220-2YE44-0AF0	CONVERTER
G120X (400V,IP20,90kW,C2,DP,BOP-2,3C2)	6SL3220-2YE44-0AP0	CONVERTER
G120X (400V,IP20,90kW,UF,USS,BOP-2,3C2)	6SL3220-2YE44-0UB0	CONVERTER
G120X (400V,IP20,90kW,UF,PN,BOP-2,3C2)	6SL3220-2YE44-0UF0	CONVERTER
G120X (400V,IP20,90kW,UF,DP,BOP-2,3C2)	6SL3220-2YE44-0UP0	CONVERTER
G120X (400V,IP20,90kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE44-1AB0	CONVERTER
G120X (400V,IP20,90kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE44-1AF0	CONVERTER
G120X (400V,IP20,90kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE44-1AP0	CONVERTER
G120X (400V,IP20,90kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE44-1UB0	CONVERTER
G120X (400V,IP20,90kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE44-1UF0	CONVERTER
G120X (400V,IP20,90kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE44-1UP0	CONVERTER
G120X (400V,IP20,110kW,C2,USS,BOP-2,3C2)	6SL3220-2YE46-0AB0	CONVERTER
G120X (400V,IP20,110kW,C2,PN,BOP-2,3C2)	6SL3220-2YE46-0AF0	CONVERTER
G120X (400V,IP20,110kW,C2,DP,BOP-2,3C2)	6SL3220-2YE46-0AP0	CONVERTER
G120X (400V,IP20,110kW,UF,USS,BOP-2,3C2)	6SL3220-2YE46-0UB0	CONVERTER
G120X (400V,IP20,110kW,UF,PN,BOP-2,3C2)	6SL3220-2YE46-0UF0	CONVERTER
G120X (400V,IP20,110kW,UF,DP,BOP-2,3C2)	6SL3220-2YE46-0UP0	CONVERTER

G120X (400V,IP20,110kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE46-1AB0	CONVERTER
G120X (400V,IP20,110kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE46-1AF0	CONVERTER
G120X (400V,IP20,110kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE46-1AP0	CONVERTER
G120X (400V,IP20,110kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE46-1UB0	CONVERTER
G120X (400V,IP20,110kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE46-1UF0	CONVERTER
G120X (400V,IP20,110kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE46-1UP0	CONVERTER
G120X (400V,IP20,132kW,C2,USS,BOP-2,3C2)	6SL3220-2YE48-0AB0	CONVERTER
G120X (400V,IP20,132kW,C2,PN,BOP-2,3C2)	6SL3220-2YE48-0AF0	CONVERTER
G120X (400V,IP20,132kW,C2,DP,BOP-2,3C2)	6SL3220-2YE48-0AP0	CONVERTER
G120X (400V,IP20,132kW,UF,USS,BOP-2,3C2)	6SL3220-2YE48-0UB0	CONVERTER
G120X (400V,IP20,132kW,UF,PN,BOP-2,3C2)	6SL3220-2YE48-0UF0	CONVERTER
G120X (400V,IP20,132kW,UF,DP,BOP-2,3C2)	6SL3220-2YE48-0UP0	CONVERTER
G120X (400V,IP20,132kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE48-1AB0	CONVERTER
G120X (400V,IP20,132kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE48-1AF0	CONVERTER
G120X (400V,IP20,132kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE48-1AP0	CONVERTER
G120X (400V,IP20,132kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YE48-1UB0	CONVERTER
G120X (400V,IP20,132kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YE48-1UF0	CONVERTER
G120X (400V,IP20,132kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YE48-1UP0	CONVERTER
G120X (400V,IP20,160kW,C2,USS,BOP-2,3C2)	6SL3220-2YE50-0AB0	CONVERTER
G120X (400V,IP20,160kW,C2,PN,BOP-2,3C2)	6SL3220-2YE50-0AF0	CONVERTER
G120X (400V,IP20,160kW,C2,DP,BOP-2,3C2)	6SL3220-2YE50-0AP0	CONVERTER
G120X (400V,IP20,160kW,C3,USS,BOP-2,3C2)	6SL3220-2YE50-0CB0	CONVERTER
G120X (400V,IP20,160kW,C3,PN,BOP-2,3C2)	6SL3220-2YE50-0CF0	CONVERTER
G120X (400V,IP20,160kW,C3,DP,BOP-2,3C2)	6SL3220-2YE50-0CP0	CONVERTER
G120X (400V,IP20,160kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE50-1AB0	CONVERTER
G120X (400V,IP20,160kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE50-1AF0	CONVERTER
G120X (400V,IP20,160kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE50-1AP0	CONVERTER
G120X (400V,IP20,160kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YE50-1CB0	CONVERTER
G120X (400V,IP20,160kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YE50-1CF0	CONVERTER
G120X (400V,IP20,160kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YE50-1CP0	CONVERTER
G120X (400V,IP20,200kW,C2,USS,BOP-2,3C2)	6SL3220-2YE52-0AB0	CONVERTER
G120X (400V,IP20,200kW,C2,PN,BOP-2,3C2)	6SL3220-2YE52-0AF0	CONVERTER
G120X (400V,IP20,200kW,C2,DP,BOP-2,3C2)	6SL3220-2YE52-0AP0	CONVERTER
G120X (400V,IP20,200kW,C3,USS,BOP-2,3C2)	6SL3220-2YE52-0CB0	CONVERTER
G120X (400V,IP20,200kW,C3,PN,BOP-2,3C2)	6SL3220-2YE52-0CF0	CONVERTER
G120X (400V,IP20,200kW,C3,DP,BOP-2,3C2)	6SL3220-2YE52-0CP0	CONVERTER
G120X (400V,IP20,200kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE52-1AB0	CONVERTER
G120X (400V,IP20,200kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE52-1AF0	CONVERTER
G120X (400V,IP20,200kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE52-1AP0	CONVERTER
G120X (400V,IP20,200kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YE52-1CB0	CONVERTER
G120X (400V,IP20,200kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YE52-1CF0	CONVERTER
G120X (400V,IP20,200kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YE52-1CP0	CONVERTER
G120X (400V,IP20,250kW,C2,USS,BOP-2,3C2)	6SL3220-2YE54-0AB0	CONVERTER
G120X (400V,IP20,250kW,C2,PN,BOP-2,3C2)	6SL3220-2YE54-0AF0	CONVERTER

G120X (400V,IP20,250kW,C2,DP,BOP-2,3C2)	6SL3220-2YE54-0AP0	CONVERTER
G120X (400V,IP20,250kW,C3,USS,BOP-2,3C2)	6SL3220-2YE54-0CB0	CONVERTER
G120X (400V,IP20,250kW,C3,PN,BOP-2,3C2)	6SL3220-2YE54-0CF0	CONVERTER
G120X (400V,IP20,250kW,C3,DP,BOP-2,3C2)	6SL3220-2YE54-0CP0	CONVERTER
G120X (400V,IP20,250kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YE54-1AB0	CONVERTER
G120X (400V,IP20,250kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YE54-1AF0	CONVERTER
G120X (400V,IP20,250kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YE54-1AP0	CONVERTER
G120X (400V,IP20,250kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YE54-1CB0	CONVERTER
G120X (400V,IP20,250kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YE54-1CF0	CONVERTER
G120X (400V,IP20,250kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YE54-1CP0	CONVERTER
G120X (400V,IP20,315kW,C3,USS,BOP-2,3C2)	6SL3220-2YE56-0CB0	CONVERTER
G120X (400V,IP20,315kW,C3,PN,BOP-2,3C2)	6SL3220-2YE56-0CF0	CONVERTER
G120X (400V,IP20,315kW,C3,DP,BOP-2,3C2)	6SL3220-2YE56-0CP0	CONVERTER
G120X (400V,IP20,315kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YE56-1CB0	CONVERTER
G120X (400V,IP20,315kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YE56-1CF0	CONVERTER
G120X (400V,IP20,315kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YE56-1CP0	CONVERTER
G120X (400V,IP20,355kW,C3,USS,BOP-2,3C2)	6SL3220-2YE58-0CB0	CONVERTER
G120X (400V,IP20,355kW,C3,PN,BOP-2,3C2)	6SL3220-2YE58-0CF0	CONVERTER
G120X (400V,IP20,355kW,C3,DP,BOP-2,3C2)	6SL3220-2YE58-0CP0	CONVERTER
G120X (400V,IP20,355kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YE58-1CB0	CONVERTER
G120X (400V,IP20,355kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YE58-1CF0	CONVERTER
G120X (400V,IP20,355kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YE58-1CP0	CONVERTER
G120X (400V,IP20,400kW,C3,USS,BOP-2,3C2)	6SL3220-2YE60-0CB0	CONVERTER
G120X (400V,IP20,400kW,C3,PN,BOP-2,3C2)	6SL3220-2YE60-0CF0	CONVERTER
G120X (400V,IP20,400kW,C3,DP,BOP-2,3C2)	6SL3220-2YE60-0CP0	CONVERTER
G120X (400V,IP20,400kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YE60-1CB0	CONVERTER
G120X (400V,IP20,400kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YE60-1CF0	CONVERTER
G120X (400V,IP20,400kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YE60-1CP0	CONVERTER
G120X (400V,IP20,450kW,C3,USS,BOP-2,3C2)	6SL3220-2YE62-0CB0	CONVERTER
G120X (400V,IP20,450kW,C3,PN,BOP-2,3C2)	6SL3220-2YE62-0CF0	CONVERTER
G120X (400V,IP20,450kW,C3,DP,BOP-2,3C2)	6SL3220-2YE62-0CP0	CONVERTER
G120X (400V,IP20,450kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YE62-1CB0	CONVERTER
G120X (400V,IP20,450kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YE62-1CF0	CONVERTER
G120X (400V,IP20,450kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YE62-1CP0	CONVERTER
G120X (400V,IP20,500kW,C3,USS,BOP-2,3C2)	6SL3220-2YE64-0CB0	CONVERTER
G120X (400V,IP20,500kW,C3,PN,BOP-2,3C2)	6SL3220-2YE64-0CF0	CONVERTER
G120X (400V,IP20,500kW,C3,DP,BOP-2,3C2)	6SL3220-2YE64-0CP0	CONVERTER
G120X (400V,IP20,500kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YE64-1CB0	CONVERTER
G120X (400V,IP20,500kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YE64-1CF0	CONVERTER
G120X (400V,IP20,500kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YE64-1CP0	CONVERTER
G120X (400V,IP20,560kW,C3,USS,BOP-2,3C2)	6SL3220-2YE66-0CB0	CONVERTER
G120X (400V,IP20,560kW,C3,PN,BOP-2,3C2)	6SL3220-2YE66-0CF0	CONVERTER
G120X (400V,IP20,560kW,C3,DP,BOP-2,3C2)	6SL3220-2YE66-0CP0	CONVERTER
G120X (400V,IP20,560kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YE66-1CB0	CONVERTER

G120X (400V,IP20,560kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YE66-1CF0	CONVERTER
G120X (400V,IP20,560kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YE66-1CP0	CONVERTER
G120X (690V,IP20,3kW,C2,USS,BOP-2,3C2)	6SL3220-2YH18-0AB0	CONVERTER
G120X (690V,IP20,3kW,C2,PN,BOP-2,3C2)	6SL3220-2YH18-0AF0	CONVERTER
G120X (690V,IP20,3kW,C2,DP,BOP-2,3C2)	6SL3220-2YH18-0AP0	CONVERTER
G120X (690V,IP20,3kW,UF,USS,BOP-2,3C2)	6SL3220-2YH18-0UB0	CONVERTER
G120X (690V,IP20,3kW,UF,PN,BOP-2,3C2)	6SL3220-2YH18-0UF0	CONVERTER
G120X (690V,IP20,3kW,UF,DP,BOP-2,3C2)	6SL3220-2YH18-0UP0	CONVERTER
G120X (690V,IP20,3kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YH18-1AB0	CONVERTER
G120X (690V,IP20,3kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YH18-1AF0	CONVERTER
G120X (690V,IP20,3kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YH18-1AP0	CONVERTER
G120X (690V,IP20,3kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH18-1UB0	CONVERTER
G120X (690V,IP20,3kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH18-1UF0	CONVERTER
G120X (690V,IP20,3kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH18-1UP0	CONVERTER
G120X (690V,IP20,4kW,C2,USS,BOP-2,3C2)	6SL3220-2YH20-0AB0	CONVERTER
G120X (690V,IP20,4kW,C2,PN,BOP-2,3C2)	6SL3220-2YH20-0AF0	CONVERTER
G120X (690V,IP20,4kW,C2,DP,BOP-2,3C2)	6SL3220-2YH20-0AP0	CONVERTER
G120X (690V,IP20,4kW,UF,USS,BOP-2,3C2)	6SL3220-2YH20-0UB0	CONVERTER
G120X (690V,IP20,4kW,UF,PN,BOP-2,3C2)	6SL3220-2YH20-0UF0	CONVERTER
G120X (690V,IP20,4kW,UF,DP,BOP-2,3C2)	6SL3220-2YH20-0UP0	CONVERTER
G120X (690V,IP20,4kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YH20-1AB0	CONVERTER
G120X (690V,IP20,4kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YH20-1AF0	CONVERTER
G120X (690V,IP20,4kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YH20-1AP0	CONVERTER
G120X (690V,IP20,4kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH20-1UB0	CONVERTER
G120X (690V,IP20,4kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH20-1UF0	CONVERTER
G120X (690V,IP20,4kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH20-1UP0	CONVERTER
G120X (690V,IP20,5.5kW,C2,USS,BOP-2,3C2)	6SL3220-2YH22-0AB0	CONVERTER
G120X (690V,IP20,5.5kW,C2,PN,BOP-2,3C2)	6SL3220-2YH22-0AF0	CONVERTER
G120X (690V,IP20,5.5kW,C2,DP,BOP-2,3C2)	6SL3220-2YH22-0AP0	CONVERTER
G120X (690V,IP20,5.5kW,UF,USS,BOP-2,3C2)	6SL3220-2YH22-0UB0	CONVERTER
G120X (690V,IP20,5.5kW,UF,PN,BOP-2,3C2)	6SL3220-2YH22-0UF0	CONVERTER
G120X (690V,IP20,5.5kW,UF,DP,BOP-2,3C2)	6SL3220-2YH22-0UP0	CONVERTER
G120X (690V,IP20,5.5kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YH22-1AB0	CONVERTER
G120X (690V,IP20,5.5kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YH22-1AF0	CONVERTER
G120X (690V,IP20,5.5kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YH22-1AP0	CONVERTER
G120X (690V,IP20,5.5kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH22-1UB0	CONVERTER
G120X (690V,IP20,5.5kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH22-1UF0	CONVERTER
G120X (690V,IP20,5.5kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH22-1UP0	CONVERTER
G120X (690V,IP20,7.5kW,C2,USS,BOP-2,3C2)	6SL3220-2YH24-0AB0	CONVERTER
G120X (690V,IP20,7.5kW,C2,PN,BOP-2,3C2)	6SL3220-2YH24-0AF0	CONVERTER
G120X (690V,IP20,7.5kW,C2,DP,BOP-2,3C2)	6SL3220-2YH24-0AP0	CONVERTER
G120X (690V,IP20,7.5kW,UF,USS,BOP-2,3C2)	6SL3220-2YH24-0UB0	CONVERTER
G120X (690V,IP20,7.5kW,UF,PN,BOP-2,3C2)	6SL3220-2YH24-0UF0	CONVERTER
G120X (690V,IP20,7.5kW,UF,DP,BOP-2,3C2)	6SL3220-2YH24-0UP0	CONVERTER

G120X (690V,IP20,7.5kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YH24-1AB0	CONVERTER
G120X (690V,IP20,7.5kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YH24-1AF0	CONVERTER
G120X (690V,IP20,7.5kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YH24-1AP0	CONVERTER
G120X (690V,IP20,7.5kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH24-1UB0	CONVERTER
G120X (690V,IP20,7.5kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH24-1UF0	CONVERTER
G120X (690V,IP20,7.5kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH24-1UP0	CONVERTER
G120X (690V,IP20,11kW,C2,USS,BOP-2,3C2)	6SL3220-2YH26-0AB0	CONVERTER
G120X (690V,IP20,11kW,C2,PN,BOP-2,3C2)	6SL3220-2YH26-0AF0	CONVERTER
G120X (690V,IP20,11kW,C2,DP,BOP-2,3C2)	6SL3220-2YH26-0AP0	CONVERTER
G120X (690V,IP20,11kW,UF,USS,BOP-2,3C2)	6SL3220-2YH26-0UB0	CONVERTER
G120X (690V,IP20,11kW,UF,PN,BOP-2,3C2)	6SL3220-2YH26-0UF0	CONVERTER
G120X (690V,IP20,11kW,UF,DP,BOP-2,3C2)	6SL3220-2YH26-0UP0	CONVERTER
G120X (690V,IP20,11kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YH26-1AB0	CONVERTER
G120X (690V,IP20,11kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YH26-1AF0	CONVERTER
G120X (690V,IP20,11kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YH26-1AP0	CONVERTER
G120X (690V,IP20,11kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH26-1UB0	CONVERTER
G120X (690V,IP20,11kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH26-1UF0	CONVERTER
G120X (690V,IP20,11kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH26-1UP0	CONVERTER
G120X (690V,IP20,15kW,C2,USS,BOP-2,3C2)	6SL3220-2YH28-0AB0	CONVERTER
G120X (690V,IP20,15kW,C2,PN,BOP-2,3C2)	6SL3220-2YH28-0AF0	CONVERTER
G120X (690V,IP20,15kW,C2,DP,BOP-2,3C2)	6SL3220-2YH28-0AP0	CONVERTER
G120X (690V,IP20,15kW,UF,USS,BOP-2,3C2)	6SL3220-2YH28-0UB0	CONVERTER
G120X (690V,IP20,15kW,UF,PN,BOP-2,3C2)	6SL3220-2YH28-0UF0	CONVERTER
G120X (690V,IP20,15kW,UF,DP,BOP-2,3C2)	6SL3220-2YH28-0UP0	CONVERTER
G120X (690V,IP20,15kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YH28-1AB0	CONVERTER
G120X (690V,IP20,15kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YH28-1AF0	CONVERTER
G120X (690V,IP20,15kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YH28-1AP0	CONVERTER
G120X (690V,IP20,15kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH28-1UB0	CONVERTER
G120X (690V,IP20,15kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH28-1UF0	CONVERTER
G120X (690V,IP20,15kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH28-1UP0	CONVERTER
G120X (690V,IP20,18,5kW,C2,USS,BOP-2,3C2)	6SL3220-2YH30-0AB0	CONVERTER
G120X (690V,IP20,18,5kW,C2,PN,BOP-2,3C2)	6SL3220-2YH30-0AF0	CONVERTER
G120X (690V,IP20,18,5kW,C2,DP,BOP-2,3C2)	6SL3220-2YH30-0AP0	CONVERTER
G120X (690V,IP20,18,5kW,UF,USS,BOP-2,3C2)	6SL3220-2YH30-0UB0	CONVERTER
G120X (690V,IP20,18,5kW,UF,PN,BOP-2,3C2)	6SL3220-2YH30-0UF0	CONVERTER
G120X (690V,IP20,18,5kW,UF,DP,BOP-2,3C2)	6SL3220-2YH30-0UP0	CONVERTER
G120X (690V,IP20,18,5kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YH30-1AB0	CONVERTER
G120X (690V,IP20,18,5kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YH30-1AF0	CONVERTER
G120X (690V,IP20,18,5kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YH30-1AP0	CONVERTER
G120X (690V,IP20,18,5kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH30-1UB0	CONVERTER
G120X (690V,IP20,18,5kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH30-1UF0	CONVERTER
G120X (690V,IP20,18,5kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH30-1UP0	CONVERTER
G120X (690V,IP20,22kW,C2,USS,BOP-2,3C2)	6SL3220-2YH32-0AB0	CONVERTER
G120X (690V,IP20,22kW,C2,PN,BOP-2,3C2)	6SL3220-2YH32-0AF0	CONVERTER

G120X (690V,IP20,22kW,C2,DP,BOP-2,3C2)	6SL3220-2YH32-0AP0	CONVERTER
G120X (690V,IP20,22kW,UF,USS,BOP-2,3C2)	6SL3220-2YH32-0UB0	CONVERTER
G120X (690V,IP20,22kW,UF,PN,BOP-2,3C2)	6SL3220-2YH32-0UF0	CONVERTER
G120X (690V,IP20,22kW,UF,DP,BOP-2,3C2)	6SL3220-2YH32-0UP0	CONVERTER
G120X (690V,IP20,22kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YH32-1AB0	CONVERTER
G120X (690V,IP20,22kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YH32-1AF0	CONVERTER
G120X (690V,IP20,22kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YH32-1AP0	CONVERTER
G120X (690V,IP20,22kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH32-1UB0	CONVERTER
G120X (690V,IP20,22kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH32-1UF0	CONVERTER
G120X (690V,IP20,22kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH32-1UP0	CONVERTER
G120X (690V,IP20,30kW,C2,USS,BOP-2,3C2)	6SL3220-2YH34-0AB0	CONVERTER
G120X (690V,IP20,30kW,C2,PN,BOP-2,3C2)	6SL3220-2YH34-0AF0	CONVERTER
G120X (690V,IP20,30kW,C2,DP,BOP-2,3C2)	6SL3220-2YH34-0AP0	CONVERTER
G120X (690V,IP20,30kW,UF,USS,BOP-2,3C2)	6SL3220-2YH34-0UB0	CONVERTER
G120X (690V,IP20,30kW,UF,PN,BOP-2,3C2)	6SL3220-2YH34-0UF0	CONVERTER
G120X (690V,IP20,30kW,UF,DP,BOP-2,3C2)	6SL3220-2YH34-0UP0	CONVERTER
G120X (690V,IP20,30kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YH34-1AB0	CONVERTER
G120X (690V,IP20,30kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YH34-1AF0	CONVERTER
G120X (690V,IP20,30kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YH34-1AP0	CONVERTER
G120X (690V,IP20,30kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH34-1UB0	CONVERTER
G120X (690V,IP20,30kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH34-1UF0	CONVERTER
G120X (690V,IP20,30kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH34-1UP0	CONVERTER
G120X (690V,IP20,37kW,C2,USS,BOP-2,3C2)	6SL3220-2YH36-0AB0	CONVERTER
G120X (690V,IP20,37kW,C2,PN,BOP-2,3C2)	6SL3220-2YH36-0AF0	CONVERTER
G120X (690V,IP20,37kW,C2,DP,BOP-2,3C2)	6SL3220-2YH36-0AP0	CONVERTER
G120X (690V,IP20,37kW,UF,USS,BOP-2,3C2)	6SL3220-2YH36-0UB0	CONVERTER
G120X (690V,IP20,37kW,UF,PN,BOP-2,3C2)	6SL3220-2YH36-0UF0	CONVERTER
G120X (690V,IP20,37kW,UF,DP,BOP-2,3C2)	6SL3220-2YH36-0UP0	CONVERTER
G120X (690V,IP20,37kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YH36-1AB0	CONVERTER
G120X (690V,IP20,37kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YH36-1AF0	CONVERTER
G120X (690V,IP20,37kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YH36-1AP0	CONVERTER
G120X (690V,IP20,37kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH36-1UB0	CONVERTER
G120X (690V,IP20,37kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH36-1UF0	CONVERTER
G120X (690V,IP20,37kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH36-1UP0	CONVERTER
G120X (690V,IP20,45kW,C2,USS,BOP-2,3C2)	6SL3220-2YH38-0AB0	CONVERTER
G120X (690V,IP20,45kW,C2,PN,BOP-2,3C2)	6SL3220-2YH38-0AF0	CONVERTER
G120X (690V,IP20,45kW,C2,DP,BOP-2,3C2)	6SL3220-2YH38-0AP0	CONVERTER
G120X (690V,IP20,45kW,UF,USS,BOP-2,3C2)	6SL3220-2YH38-0UB0	CONVERTER
G120X (690V,IP20,45kW,UF,PN,BOP-2,3C2)	6SL3220-2YH38-0UF0	CONVERTER
G120X (690V,IP20,45kW,UF,DP,BOP-2,3C2)	6SL3220-2YH38-0UP0	CONVERTER
G120X (690V,IP20,45kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YH38-1AB0	CONVERTER
G120X (690V,IP20,45kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YH38-1AF0	CONVERTER
G120X (690V,IP20,45kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YH38-1AP0	CONVERTER
G120X (690V,IP20,45kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH38-1UB0	CONVERTER

G120X (690V,IP20,45kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH38-1UF0	CONVERTER
G120X (690V,IP20,45kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH38-1UP0	CONVERTER
G120X (690V,IP20,55kW,C2,USS,BOP-2,3C2)	6SL3220-2YH40-0AB0	CONVERTER
G120X (690V,IP20,55kW,C2,PN,BOP-2,3C2)	6SL3220-2YH40-0AF0	CONVERTER
G120X (690V,IP20,55kW,C2,DP,BOP-2,3C2)	6SL3220-2YH40-0AP0	CONVERTER
G120X (690V,IP20,55kW,UF,USS,BOP-2,3C2)	6SL3220-2YH40-0UB0	CONVERTER
G120X (690V,IP20,55kW,UF,PN,BOP-2,3C2)	6SL3220-2YH40-0UF0	CONVERTER
G120X (690V,IP20,55kW,UF,DP,BOP-2,3C2)	6SL3220-2YH40-0UP0	CONVERTER
G120X (690V,IP20,55kW,C2,USS,BOP-2,3C2,IO)	6SL3220-2YH40-1AB0	CONVERTER
G120X (690V,IP20,55kW,C2,PN,BOP-2,3C2,IO)	6SL3220-2YH40-1AF0	CONVERTER
G120X (690V,IP20,55kW,C2,DP,BOP-2,3C2,IO)	6SL3220-2YH40-1AP0	CONVERTER
G120X (690V,IP20,55kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH40-1UB0	CONVERTER
G120X (690V,IP20,55kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH40-1UF0	CONVERTER
G120X (690V,IP20,55kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH40-1UP0	CONVERTER
G120X (690V,IP20,75kW,C3,USS,BOP-2,3C2)	6SL3220-2YH42-0CB0	CONVERTER
G120X (690V,IP20,75kW,C3,PN,BOP-2,3C2)	6SL3220-2YH42-0CF0	CONVERTER
G120X (690V,IP20,75kW,C3,DP,BOP-2,3C2)	6SL3220-2YH42-0CP0	CONVERTER
G120X (690V,IP20,75kW,UF,USS,BOP-2,3C2)	6SL3220-2YH42-0UB0	CONVERTER
G120X (690V,IP20,75kW,UF,PN,BOP-2,3C2)	6SL3220-2YH42-0UF0	CONVERTER
G120X (690V,IP20,75kW,UF,DP,BOP-2,3C2)	6SL3220-2YH42-0UP0	CONVERTER
G120X (690V,IP20,75kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YH42-1CB0	CONVERTER
G120X (690V,IP20,75kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YH42-1CF0	CONVERTER
G120X (690V,IP20,75kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YH42-1CP0	CONVERTER
G120X (690V,IP20,75kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH42-1UB0	CONVERTER
G120X (690V,IP20,75kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH42-1UF0	CONVERTER
G120X (690V,IP20,75kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH42-1UP0	CONVERTER
G120X (690V,IP20,90kW,C3,USS,BOP-2,3C2)	6SL3220-2YH44-0CB0	CONVERTER
G120X (690V,IP20,90kW,C3,PN,BOP-2,3C2)	6SL3220-2YH44-0CF0	CONVERTER
G120X (690V,IP20,90kW,C3,DP,BOP-2,3C2)	6SL3220-2YH44-0CP0	CONVERTER
G120X (690V,IP20,90kW,UF,USS,BOP-2,3C2)	6SL3220-2YH44-0UB0	CONVERTER
G120X (690V,IP20,90kW,UF,PN,BOP-2,3C2)	6SL3220-2YH44-0UF0	CONVERTER
G120X (690V,IP20,90kW,UF,DP,BOP-2,3C2)	6SL3220-2YH44-0UP0	CONVERTER
G120X (690V,IP20,90kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YH44-1CB0	CONVERTER
G120X (690V,IP20,90kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YH44-1CF0	CONVERTER
G120X (690V,IP20,90kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YH44-1CP0	CONVERTER
G120X (690V,IP20,90kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH44-1UB0	CONVERTER
G120X (690V,IP20,90kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH44-1UF0	CONVERTER
G120X (690V,IP20,90kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH44-1UP0	CONVERTER
G120X (690V,IP20,110kW,C3,USS,BOP-2,3C2)	6SL3220-2YH46-0CB0	CONVERTER
G120X (690V,IP20,110kW,C3,PN,BOP-2,3C2)	6SL3220-2YH46-0CF0	CONVERTER
G120X (690V,IP20,110kW,C3,DP,BOP-2,3C2)	6SL3220-2YH46-0CP0	CONVERTER
G120X (690V,IP20,110kW,UF,USS,BOP-2,3C2)	6SL3220-2YH46-0UB0	CONVERTER
G120X (690V,IP20,110kW,UF,PN,BOP-2,3C2)	6SL3220-2YH46-0UF0	CONVERTER
G120X (690V,IP20,110kW,UF,DP,BOP-2,3C2)	6SL3220-2YH46-0UP0	CONVERTER

G120X (690V,IP20,110kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YH46-1CB0	CONVERTER
G120X (690V,IP20,110kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YH46-1CF0	CONVERTER
G120X (690V,IP20,110kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YH46-1CP0	CONVERTER
G120X (690V,IP20,110kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH46-1UB0	CONVERTER
G120X (690V,IP20,110kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH46-1UF0	CONVERTER
G120X (690V,IP20,110kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH46-1UP0	CONVERTER
G120X (690V,IP20,132kW,C3,USS,BOP-2,3C2)	6SL3220-2YH48-0CB0	CONVERTER
G120X (690V,IP20,132kW,C3,PN,BOP-2,3C2)	6SL3220-2YH48-0CF0	CONVERTER
G120X (690V,IP20,132kW,C3,DP,BOP-2,3C2)	6SL3220-2YH48-0CP0	CONVERTER
G120X (690V,IP20,132kW,UF,USS,BOP-2,3C2)	6SL3220-2YH48-0UB0	CONVERTER
G120X (690V,IP20,132kW,UF,PN,BOP-2,3C2)	6SL3220-2YH48-0UF0	CONVERTER
G120X (690V,IP20,132kW,UF,DP,BOP-2,3C2)	6SL3220-2YH48-0UP0	CONVERTER
G120X (690V,IP20,132kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YH48-1CB0	CONVERTER
G120X (690V,IP20,132kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YH48-1CF0	CONVERTER
G120X (690V,IP20,132kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YH48-1CP0	CONVERTER
G120X (690V,IP20,132kW,UF,USS,BOP-2,3C2,IO)	6SL3220-2YH48-1UB0	CONVERTER
G120X (690V,IP20,132kW,UF,PN,BOP-2,3C2,IO)	6SL3220-2YH48-1UF0	CONVERTER
G120X (690V,IP20,132kW,UF,DP,BOP-2,3C2,IO)	6SL3220-2YH48-1UP0	CONVERTER
G120X (690V,IP20,160kW,C3,USS,BOP-2,3C2)	6SL3220-2YH50-0CB0	CONVERTER
G120X (690V,IP20,160kW,C3,PN,BOP-2,3C2)	6SL3220-2YH50-0CF0	CONVERTER
G120X (690V,IP20,160kW,C3,DP,BOP-2,3C2)	6SL3220-2YH50-0CP0	CONVERTER
G120X (690V,IP20,160kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YH50-1CB0	CONVERTER
G120X (690V,IP20,160kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YH50-1CF0	CONVERTER
G120X (690V,IP20,160kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YH50-1CP0	CONVERTER
G120X (690V,IP20,200kW,C3,USS,BOP-2,3C2)	6SL3220-2YH52-0CB0	CONVERTER
G120X (690V,IP20,200kW,C3,PN,BOP-2,3C2)	6SL3220-2YH52-0CF0	CONVERTER
G120X (690V,IP20,200kW,C3,DP,BOP-2,3C2)	6SL3220-2YH52-0CP0	CONVERTER
G120X (690V,IP20,200kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YH52-1CB0	CONVERTER
G120X (690V,IP20,200kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YH52-1CF0	CONVERTER
G120X (690V,IP20,200kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YH52-1CP0	CONVERTER
G120X (690V,IP20,250kW,C3,USS,BOP-2,3C2)	6SL3220-2YH54-0CB0	CONVERTER
G120X (690V,IP20,250kW,C3,PN,BOP-2,3C2)	6SL3220-2YH54-0CF0	CONVERTER
G120X (690V,IP20,250kW,C3,DP,BOP-2,3C2)	6SL3220-2YH54-0CP0	CONVERTER
G120X (690V,IP20,250kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YH54-1CB0	CONVERTER
G120X (690V,IP20,250kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YH54-1CF0	CONVERTER
G120X (690V,IP20,250kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YH54-1CP0	CONVERTER
G120X (690V,IP20,315kW,C3,USS,BOP-2,3C2)	6SL3220-2YH56-0CB0	CONVERTER
G120X (690V,IP20,315kW,C3,PN,BOP-2,3C2)	6SL3220-2YH56-0CF0	CONVERTER
G120X (690V,IP20,315kW,C3,DP,BOP-2,3C2)	6SL3220-2YH56-0CP0	CONVERTER
G120X (690V,IP20,315kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YH56-1CB0	CONVERTER
G120X (690V,IP20,315kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YH56-1CF0	CONVERTER
G120X (690V,IP20,315kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YH56-1CP0	CONVERTER
G120X (690V,IP20,355kW,C3,USS,BOP-2,3C2)	6SL3220-2YH58-0CB0	CONVERTER
G120X (690V,IP20,355kW,C3,PN,BOP-2,3C2)	6SL3220-2YH58-0CF0	CONVERTER

G120X (690V,IP20,355kW,C3,DP,BOP-2,3C2)	6SL3220-2YH58-0CP0	CONVERTER
G120X (690V,IP20,355kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YH58-1CB0	CONVERTER
G120X (690V,IP20,355kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YH58-1CF0	CONVERTER
G120X (690V,IP20,355kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YH58-1CP0	CONVERTER
G120X (690V,IP20,400kW,C3,USS,BOP-2,3C2)	6SL3220-2YH60-0CB0	CONVERTER
G120X (690V,IP20,400kW,C3,PN,BOP-2,3C2)	6SL3220-2YH60-0CF0	CONVERTER
G120X (690V,IP20,400kW,C3,DP,BOP-2,3C2)	6SL3220-2YH60-0CP0	CONVERTER
G120X (690V,IP20,400kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YH60-1CB0	CONVERTER
G120X (690V,IP20,400kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YH60-1CF0	CONVERTER
G120X (690V,IP20,400kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YH60-1CP0	CONVERTER
G120X (690V,IP20,450kW,C3,USS,BOP-2,3C2)	6SL3220-2YH62-0CB0	CONVERTER
G120X (690V,IP20,450kW,C3,PN,BOP-2,3C2)	6SL3220-2YH62-0CF0	CONVERTER
G120X (690V,IP20,450kW,C3,DP,BOP-2,3C2)	6SL3220-2YH62-0CP0	CONVERTER
G120X (690V,IP20,450kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YH62-1CB0	CONVERTER
G120X (690V,IP20,450kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YH62-1CF0	CONVERTER
G120X (690V,IP20,450kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YH62-1CP0	CONVERTER
G120X (690V,IP20,500kW,C3,USS,BOP-2,3C2)	6SL3220-2YH64-0CB0	CONVERTER
G120X (690V,IP20,500kW,C3,PN,BOP-2,3C2)	6SL3220-2YH64-0CF0	CONVERTER
G120X (690V,IP20,500kW,C3,DP,BOP-2,3C2)	6SL3220-2YH64-0CP0	CONVERTER
G120X (690V,IP20,500kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YH64-1CB0	CONVERTER
G120X (690V,IP20,500kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YH64-1CF0	CONVERTER
G120X (690V,IP20,500kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YH64-1CP0	CONVERTER
G120X (690V,IP20,560kW,C3,USS,BOP-2,3C2)	6SL3220-2YH66-0CB0	CONVERTER
G120X (690V,IP20,560kW,C3,PN,BOP-2,3C2)	6SL3220-2YH66-0CF0	CONVERTER
G120X (690V,IP20,560kW,C3,DP,BOP-2,3C2)	6SL3220-2YH66-0CP0	CONVERTER
G120X (690V,IP20,560kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YH66-1CB0	CONVERTER
G120X (690V,IP20,560kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YH66-1CF0	CONVERTER
G120X (690V,IP20,560kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YH66-1CP0	CONVERTER
G120X (690V,IP20,630kW,C3,USS,BOP-2,3C2)	6SL3220-2YH68-0CB0	CONVERTER
G120X (690V,IP20,630kW,C3,PN,BOP-2,3C2)	6SL3220-2YH68-0CF0	CONVERTER
G120X (690V,IP20,630kW,C3,DP,BOP-2,3C2)	6SL3220-2YH68-0CP0	CONVERTER
G120X (690V,IP20,630kW,C3,USS,BOP-2,3C2,IO)	6SL3220-2YH68-1CB0	CONVERTER
G120X (690V,IP20,630kW,C3,PN,BOP-2,3C2,IO)	6SL3220-2YH68-1CF0	CONVERTER
G120X (690V,IP20,630kW,C3,DP,BOP-2,3C2,IO)	6SL3220-2YH68-1CP0	CONVERTER
G120X (230V,IP20,0.75kW,UF,USS,IOP-2,3C2)	6SL3220-3YC10-0UB0	CONVERTER
G120X (230V,IP20,0.75kW,UF,PN,IOP-2,3C2)	6SL3220-3YC10-0UF0	CONVERTER
G120X (230V,IP20,0.75kW,UF,DP,IOP-2,3C2)	6SL3220-3YC10-0UP0	CONVERTER
G120X (230V,IP20,0.75kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC10-1UB0	CONVERTER
G120X (230V,IP20,0.75kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC10-1UF0	CONVERTER
G120X (230V,IP20,0.75kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC10-1UP0	CONVERTER
G120X (230V,IP20,1.1kW,UF,USS,IOP-2,3C2)	6SL3220-3YC12-0UB0	CONVERTER
G120X (230V,IP20,1.1kW,UF,PN,IOP-2,3C2)	6SL3220-3YC12-0UF0	CONVERTER
G120X (230V,IP20,1.1kW,UF,DP,IOP-2,3C2)	6SL3220-3YC12-0UP0	CONVERTER
G120X (230V,IP20,1.1kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC12-1UB0	CONVERTER

G120X (230V,IP20,1.1kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC12-1UF0	CONVERTER
G120X (230V,IP20,1.1kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC12-1UP0	CONVERTER
G120X (230V,IP20,1.5kW,UF,USS,IOP-2,3C2)	6SL3220-3YC14-0UB0	CONVERTER
G120X (230V,IP20,1.5kW,UF,PN,IOP-2,3C2)	6SL3220-3YC14-0UF0	CONVERTER
G120X (230V,IP20,1.5kW,UF,DP,IOP-2,3C2)	6SL3220-3YC14-0UP0	CONVERTER
G120X (230V,IP20,1.5kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC14-1UB0	CONVERTER
G120X (230V,IP20,1.5kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC14-1UF0	CONVERTER
G120X (230V,IP20,1.5kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC14-1UP0	CONVERTER
G120X (230V,IP20,2.2kW,UF,USS,IOP-2,3C2)	6SL3220-3YC16-0UB0	CONVERTER
G120X (230V,IP20,2.2kW,UF,PN,IOP-2,3C2)	6SL3220-3YC16-0UF0	CONVERTER
G120X (230V,IP20,2.2kW,UF,DP,IOP-2,3C2)	6SL3220-3YC16-0UP0	CONVERTER
G120X (230V,IP20,2.2kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC16-1UB0	CONVERTER
G120X (230V,IP20,2.2kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC16-1UF0	CONVERTER
G120X (230V,IP20,2.2kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC16-1UP0	CONVERTER
G120X (230V,IP20,3kW,UF,USS,IOP-2,3C2)	6SL3220-3YC18-0UB0	CONVERTER
G120X (230V,IP20,3kW,UF,PN,IOP-2,3C2)	6SL3220-3YC18-0UF0	CONVERTER
G120X (230V,IP20,3kW,UF,DP,IOP-2,3C2)	6SL3220-3YC18-0UP0	CONVERTER
G120X (230V,IP20,3kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC18-1UB0	CONVERTER
G120X (230V,IP20,3kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC18-1UF0	CONVERTER
G120X (230V,IP20,3kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC18-1UP0	CONVERTER
G120X (230V,IP20,4kW,UF,USS,IOP-2,3C2)	6SL3220-3YC20-0UB0	CONVERTER
G120X (230V,IP20,4kW,UF,PN,IOP-2,3C2)	6SL3220-3YC20-0UF0	CONVERTER
G120X (230V,IP20,4kW,UF,DP,IOP-2,3C2)	6SL3220-3YC20-0UP0	CONVERTER
G120X (230V,IP20,4kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC20-1UB0	CONVERTER
G120X (230V,IP20,4kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC20-1UF0	CONVERTER
G120X (230V,IP20,4kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC20-1UP0	CONVERTER
G120X (230V,IP20,5.5kW,UF,USS,IOP-2,3C2)	6SL3220-3YC22-0UB0	CONVERTER
G120X (230V,IP20,5.5kW,UF,PN,IOP-2,3C2)	6SL3220-3YC22-0UF0	CONVERTER
G120X (230V,IP20,5.5kW,UF,DP,IOP-2,3C2)	6SL3220-3YC22-0UP0	CONVERTER
G120X (230V,IP20,5.5kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC22-1UB0	CONVERTER
G120X (230V,IP20,5.5kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC22-1UF0	CONVERTER
G120X (230V,IP20,5.5kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC22-1UP0	CONVERTER
G120X (230V,IP20,7.5kW,UF,USS,IOP-2,3C2)	6SL3220-3YC24-0UB0	CONVERTER
G120X (230V,IP20,7.5kW,UF,PN,IOP-2,3C2)	6SL3220-3YC24-0UF0	CONVERTER
G120X (230V,IP20,7.5kW,UF,DP,IOP-2,3C2)	6SL3220-3YC24-0UP0	CONVERTER
G120X (230V,IP20,7.5kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC24-1UB0	CONVERTER
G120X (230V,IP20,7.5kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC24-1UF0	CONVERTER
G120X (230V,IP20,7.5kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC24-1UP0	CONVERTER
G120X (230V,IP20,11kW,UF,USS,IOP-2,3C2)	6SL3220-3YC26-0UB0	CONVERTER
G120X (230V,IP20,11kW,UF,PN,IOP-2,3C2)	6SL3220-3YC26-0UF0	CONVERTER
G120X (230V,IP20,11kW,UF,DP,IOP-2,3C2)	6SL3220-3YC26-0UP0	CONVERTER
G120X (230V,IP20,11kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC26-1UB0	CONVERTER
G120X (230V,IP20,11kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC26-1UF0	CONVERTER
G120X (230V,IP20,11kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC26-1UP0	CONVERTER

G120X (230V,IP20,15kW,UF,USS,IOP-2,3C2)	6SL3220-3YC28-0UB0	CONVERTER
G120X (230V,IP20,15kW,UF,PN,IOP-2,3C2)	6SL3220-3YC28-0UF0	CONVERTER
G120X (230V,IP20,15kW,UF,DP,IOP-2,3C2)	6SL3220-3YC28-0UP0	CONVERTER
G120X (230V,IP20,15kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC28-1UB0	CONVERTER
G120X (230V,IP20,15kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC28-1UF0	CONVERTER
G120X (230V,IP20,15kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC28-1UP0	CONVERTER
G120X (230V,IP20,18,5kW,UF,USS,IOP-2,3C2)	6SL3220-3YC30-0UB0	CONVERTER
G120X (230V,IP20,18,5kW,UF,PN,IOP-2,3C2)	6SL3220-3YC30-0UF0	CONVERTER
G120X (230V,IP20,18,5kW,UF,DP,IOP-2,3C2)	6SL3220-3YC30-0UP0	CONVERTER
G120X (230V,IP20,18,5kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC30-1UB0	CONVERTER
G120X (230V,IP20,18,5kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC30-1UF0	CONVERTER
G120X (230V,IP20,18,5kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC30-1UP0	CONVERTER
G120X (230V,IP20,22kW,UF,USS,IOP-2,3C2)	6SL3220-3YC32-0UB0	CONVERTER
G120X (230V,IP20,22kW,UF,PN,IOP-2,3C2)	6SL3220-3YC32-0UF0	CONVERTER
G120X (230V,IP20,22kW,UF,DP,IOP-2,3C2)	6SL3220-3YC32-0UP0	CONVERTER
G120X (230V,IP20,22kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC32-1UB0	CONVERTER
G120X (230V,IP20,22kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC32-1UF0	CONVERTER
G120X (230V,IP20,22kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC32-1UP0	CONVERTER
G120X (230V,IP20,30kW,UF,USS,IOP-2,3C2)	6SL3220-3YC34-0UB0	CONVERTER
G120X (230V,IP20,30kW,UF,PN,IOP-2,3C2)	6SL3220-3YC34-0UF0	CONVERTER
G120X (230V,IP20,30kW,UF,DP,IOP-2,3C2)	6SL3220-3YC34-0UP0	CONVERTER
G120X (230V,IP20,30kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC34-1UB0	CONVERTER
G120X (230V,IP20,30kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC34-1UF0	CONVERTER
G120X (230V,IP20,30kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC34-1UP0	CONVERTER
G120X (230V,IP20,37kW,UF,USS,IOP-2,3C2)	6SL3220-3YC36-0UB0	CONVERTER
G120X (230V,IP20,37kW,UF,PN,IOP-2,3C2)	6SL3220-3YC36-0UF0	CONVERTER
G120X (230V,IP20,37kW,UF,DP,IOP-2,3C2)	6SL3220-3YC36-0UP0	CONVERTER
G120X (230V,IP20,37kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC36-1UB0	CONVERTER
G120X (230V,IP20,37kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC36-1UF0	CONVERTER
G120X (230V,IP20,37kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC36-1UP0	CONVERTER
G120X (230V,IP20,45kW,UF,USS,IOP-2,3C2)	6SL3220-3YC38-0UB0	CONVERTER
G120X (230V,IP20,45kW,UF,PN,IOP-2,3C2)	6SL3220-3YC38-0UF0	CONVERTER
G120X (230V,IP20,45kW,UF,DP,IOP-2,3C2)	6SL3220-3YC38-0UP0	CONVERTER
G120X (230V,IP20,45kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC38-1UB0	CONVERTER
G120X (230V,IP20,45kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC38-1UF0	CONVERTER
G120X (230V,IP20,45kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC38-1UP0	CONVERTER
G120X (230V,IP20,55kW,UF,USS,IOP-2,3C2)	6SL3220-3YC40-0UB0	CONVERTER
G120X (230V,IP20,55kW,UF,PN,IOP-2,3C2)	6SL3220-3YC40-0UF0	CONVERTER
G120X (230V,IP20,55kW,UF,DP,IOP-2,3C2)	6SL3220-3YC40-0UP0	CONVERTER
G120X (230V,IP20,55kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YC40-1UB0	CONVERTER
G120X (230V,IP20,55kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YC40-1UF0	CONVERTER
G120X (230V,IP20,55kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YC40-1UP0	CONVERTER
G120X (400V,IP20,0.75kW,C2,USS,IOP-2,3C2)	6SL3220-3YE10-0AB0	CONVERTER
G120X (400V,IP20,0.75kW,C2,PN,IOP-2,3C2)	6SL3220-3YE10-0AF0	CONVERTER

G120X (400V,IP20,0.75kW,C2,DP,IOP-2,3C2)	6SL3220-3YE10-0AP0	CONVERTER
G120X (400V,IP20,0.75kW,UF,USS,IOP-2,3C2)	6SL3220-3YE10-0UB0	CONVERTER
G120X (400V,IP20,0.75kW,UF,PN,IOP-2,3C2)	6SL3220-3YE10-0UF0	CONVERTER
G120X (400V,IP20,0.75kW,UF,DP,IOP-2,3C2)	6SL3220-3YE10-0UP0	CONVERTER
G120X (400V,IP20,0.75kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE10-1AB0	CONVERTER
G120X (400V,IP20,0.75kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE10-1AF0	CONVERTER
G120X (400V,IP20,0.75kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE10-1AP0	CONVERTER
G120X (400V,IP20,0.75kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE10-1UB0	CONVERTER
G120X (400V,IP20,0.75kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE10-1UF0	CONVERTER
G120X (400V,IP20,0.75kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE10-1UP0	CONVERTER
G120X (400V,IP20,1.1kW,C2,USS,IOP-2,3C2)	6SL3220-3YE12-0AB0	CONVERTER
G120X (400V,IP20,1.1kW,C2,PN,IOP-2,3C2)	6SL3220-3YE12-0AF0	CONVERTER
G120X (400V,IP20,1.1kW,C2,DP,IOP-2,3C2)	6SL3220-3YE12-0AP0	CONVERTER
G120X (400V,IP20,1.1kW,UF,USS,IOP-2,3C2)	6SL3220-3YE12-0UB0	CONVERTER
G120X (400V,IP20,1.1kW,UF,PN,IOP-2,3C2)	6SL3220-3YE12-0UF0	CONVERTER
G120X (400V,IP20,1.1kW,UF,DP,IOP-2,3C2)	6SL3220-3YE12-0UP0	CONVERTER
G120X (400V,IP20,1.1kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE12-1AB0	CONVERTER
G120X (400V,IP20,1.1kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE12-1AF0	CONVERTER
G120X (400V,IP20,1.1kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE12-1AP0	CONVERTER
G120X (400V,IP20,1.1kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE12-1UB0	CONVERTER
G120X (400V,IP20,1.1kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE12-1UF0	CONVERTER
G120X (400V,IP20,1.1kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE12-1UP0	CONVERTER
G120X (400V,IP20,1.5kW,C2,USS,IOP-2,3C2)	6SL3220-3YE14-0AB0	CONVERTER
G120X (400V,IP20,1.5kW,C2,PN,IOP-2,3C2)	6SL3220-3YE14-0AF0	CONVERTER
G120X (400V,IP20,1.5kW,C2,DP,IOP-2,3C2)	6SL3220-3YE14-0AP0	CONVERTER
G120X (400V,IP20,1.5kW,UF,USS,IOP-2,3C2)	6SL3220-3YE14-0UB0	CONVERTER
G120X (400V,IP20,1.5kW,UF,PN,IOP-2,3C2)	6SL3220-3YE14-0UF0	CONVERTER
G120X (400V,IP20,1.5kW,UF,DP,IOP-2,3C2)	6SL3220-3YE14-0UP0	CONVERTER
G120X (400V,IP20,1.5kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE14-1AB0	CONVERTER
G120X (400V,IP20,1.5kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE14-1AF0	CONVERTER
G120X (400V,IP20,1.5kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE14-1AP0	CONVERTER
G120X (400V,IP20,1.5kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE14-1UB0	CONVERTER
G120X (400V,IP20,1.5kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE14-1UF0	CONVERTER
G120X (400V,IP20,1.5kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE14-1UP0	CONVERTER
G120X (400V,IP20,2.2kW,C2,USS,IOP-2,3C2)	6SL3220-3YE16-0AB0	CONVERTER
G120X (400V,IP20,2.2kW,C2,PN,IOP-2,3C2)	6SL3220-3YE16-0AF0	CONVERTER
G120X (400V,IP20,2.2kW,C2,DP,IOP-2,3C2)	6SL3220-3YE16-0AP0	CONVERTER
G120X (400V,IP20,2.2kW,UF,USS,IOP-2,3C2)	6SL3220-3YE16-0UB0	CONVERTER
G120X (400V,IP20,2.2kW,UF,PN,IOP-2,3C2)	6SL3220-3YE16-0UF0	CONVERTER
G120X (400V,IP20,2.2kW,UF,DP,IOP-2,3C2)	6SL3220-3YE16-0UP0	CONVERTER
G120X (400V,IP20,2.2kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE16-1AB0	CONVERTER
G120X (400V,IP20,2.2kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE16-1AF0	CONVERTER
G120X (400V,IP20,2.2kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE16-1AP0	CONVERTER
G120X (400V,IP20,2.2kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE16-1UB0	CONVERTER

G120X (400V,IP20,2.2kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE16-1UF0	CONVERTER
G120X (400V,IP20,2.2kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE16-1UP0	CONVERTER
G120X (400V,IP20,3kW,C2,USS,IOP-2,3C2)	6SL3220-3YE18-0AB0	CONVERTER
G120X (400V,IP20,3kW,C2,PN,IOP-2,3C2)	6SL3220-3YE18-0AF0	CONVERTER
G120X (400V,IP20,3kW,C2,DP,IOP-2,3C2)	6SL3220-3YE18-0AP0	CONVERTER
G120X (400V,IP20,3kW,UF,USS,IOP-2,3C2)	6SL3220-3YE18-0UB0	CONVERTER
G120X (400V,IP20,3kW,UF,PN,IOP-2,3C2)	6SL3220-3YE18-0UF0	CONVERTER
G120X (400V,IP20,3kW,UF,DP,IOP-2,3C2)	6SL3220-3YE18-0UP0	CONVERTER
G120X (400V,IP20,3kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE18-1AB0	CONVERTER
G120X (400V,IP20,3kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE18-1AF0	CONVERTER
G120X (400V,IP20,3kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE18-1AP0	CONVERTER
G120X (400V,IP20,3kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE18-1UB0	CONVERTER
G120X (400V,IP20,3kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE18-1UF0	CONVERTER
G120X (400V,IP20,3kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE18-1UP0	CONVERTER
G120X (400V,IP20,4kW,C2,USS,IOP-2,3C2)	6SL3220-3YE20-0AB0	CONVERTER
G120X (400V,IP20,4kW,C2,PN,IOP-2,3C2)	6SL3220-3YE20-0AF0	CONVERTER
G120X (400V,IP20,4kW,C2,DP,IOP-2,3C2)	6SL3220-3YE20-0AP0	CONVERTER
G120X (400V,IP20,4kW,UF,USS,IOP-2,3C2)	6SL3220-3YE20-0UB0	CONVERTER
G120X (400V,IP20,4kW,UF,PN,IOP-2,3C2)	6SL3220-3YE20-0UF0	CONVERTER
G120X (400V,IP20,4kW,UF,DP,IOP-2,3C2)	6SL3220-3YE20-0UP0	CONVERTER
G120X (400V,IP20,4kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE20-1AB0	CONVERTER
G120X (400V,IP20,4kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE20-1AF0	CONVERTER
G120X (400V,IP20,4kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE20-1AP0	CONVERTER
G120X (400V,IP20,4kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE20-1UB0	CONVERTER
G120X (400V,IP20,4kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE20-1UF0	CONVERTER
G120X (400V,IP20,4kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE20-1UP0	CONVERTER
G120X (400V,IP20,5.5kW,C2,USS,IOP-2,3C2)	6SL3220-3YE22-0AB0	CONVERTER
G120X (400V,IP20,5.5kW,C2,PN,IOP-2,3C2)	6SL3220-3YE22-0AF0	CONVERTER
G120X (400V,IP20,5.5kW,C2,DP,IOP-2,3C2)	6SL3220-3YE22-0AP0	CONVERTER
G120X (400V,IP20,5.5kW,UF,USS,IOP-2,3C2)	6SL3220-3YE22-0UB0	CONVERTER
G120X (400V,IP20,5.5kW,UF,PN,IOP-2,3C2)	6SL3220-3YE22-0UF0	CONVERTER
G120X (400V,IP20,5.5kW,UF,DP,IOP-2,3C2)	6SL3220-3YE22-0UP0	CONVERTER
G120X (400V,IP20,5.5kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE22-1AB0	CONVERTER
G120X (400V,IP20,5.5kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE22-1AF0	CONVERTER
G120X (400V,IP20,5.5kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE22-1AP0	CONVERTER
G120X (400V,IP20,5.5kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE22-1UB0	CONVERTER
G120X (400V,IP20,5.5kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE22-1UF0	CONVERTER
G120X (400V,IP20,5.5kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE22-1UP0	CONVERTER
G120X (400V,IP20,7.5kW,C2,USS,IOP-2,3C2)	6SL3220-3YE24-0AB0	CONVERTER
G120X (400V,IP20,7.5kW,C2,PN,IOP-2,3C2)	6SL3220-3YE24-0AF0	CONVERTER
G120X (400V,IP20,7.5kW,C2,DP,IOP-2,3C2)	6SL3220-3YE24-0AP0	CONVERTER
G120X (400V,IP20,7.5kW,UF,USS,IOP-2,3C2)	6SL3220-3YE24-0UB0	CONVERTER
G120X (400V,IP20,7.5kW,UF,PN,IOP-2,3C2)	6SL3220-3YE24-0UF0	CONVERTER
G120X (400V,IP20,7.5kW,UF,DP,IOP-2,3C2)	6SL3220-3YE24-0UP0	CONVERTER

G120X (400V,IP20,7.5kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE24-1AB0	CONVERTER
G120X (400V,IP20,7.5kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE24-1AF0	CONVERTER
G120X (400V,IP20,7.5kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE24-1AP0	CONVERTER
G120X (400V,IP20,7.5kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE24-1UB0	CONVERTER
G120X (400V,IP20,7.5kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE24-1UF0	CONVERTER
G120X (400V,IP20,7.5kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE24-1UP0	CONVERTER
G120X (400V,IP20,11kW,C2,USS,IOP-2,3C2)	6SL3220-3YE26-0AB0	CONVERTER
G120X (400V,IP20,11kW,C2,PN,IOP-2,3C2)	6SL3220-3YE26-0AF0	CONVERTER
G120X (400V,IP20,11kW,C2,DP,IOP-2,3C2)	6SL3220-3YE26-0AP0	CONVERTER
G120X (400V,IP20,11kW,UF,USS,IOP-2,3C2)	6SL3220-3YE26-0UB0	CONVERTER
G120X (400V,IP20,11kW,UF,PN,IOP-2,3C2)	6SL3220-3YE26-0UF0	CONVERTER
G120X (400V,IP20,11kW,UF,DP,IOP-2,3C2)	6SL3220-3YE26-0UP0	CONVERTER
G120X (400V,IP20,11kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE26-1AB0	CONVERTER
G120X (400V,IP20,11kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE26-1AF0	CONVERTER
G120X (400V,IP20,11kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE26-1AP0	CONVERTER
G120X (400V,IP20,11kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE26-1UB0	CONVERTER
G120X (400V,IP20,11kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE26-1UF0	CONVERTER
G120X (400V,IP20,11kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE26-1UP0	CONVERTER
G120X (400V,IP20,15kW,C2,USS,IOP-2,3C2)	6SL3220-3YE28-0AB0	CONVERTER
G120X (400V,IP20,15kW,C2,PN,IOP-2,3C2)	6SL3220-3YE28-0AF0	CONVERTER
G120X (400V,IP20,15kW,C2,DP,IOP-2,3C2)	6SL3220-3YE28-0AP0	CONVERTER
G120X (400V,IP20,15kW,UF,USS,IOP-2,3C2)	6SL3220-3YE28-0UB0	CONVERTER
G120X (400V,IP20,15kW,UF,PN,IOP-2,3C2)	6SL3220-3YE28-0UF0	CONVERTER
G120X (400V,IP20,15kW,UF,DP,IOP-2,3C2)	6SL3220-3YE28-0UP0	CONVERTER
G120X (400V,IP20,15kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE28-1AB0	CONVERTER
G120X (400V,IP20,15kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE28-1AF0	CONVERTER
G120X (400V,IP20,15kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE28-1AP0	CONVERTER
G120X (400V,IP20,15kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE28-1UB0	CONVERTER
G120X (400V,IP20,15kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE28-1UF0	CONVERTER
G120X (400V,IP20,15kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE28-1UP0	CONVERTER
G120X (400V,IP20,18,5kW,C2,USS,IOP-2,3C2)	6SL3220-3YE30-0AB0	CONVERTER
G120X (400V,IP20,18,5kW,C2,PN,IOP-2,3C2)	6SL3220-3YE30-0AF0	CONVERTER
G120X (400V,IP20,18,5kW,C2,DP,IOP-2,3C2)	6SL3220-3YE30-0AP0	CONVERTER
G120X (400V,IP20,18,5kW,UF,USS,IOP-2,3C2)	6SL3220-3YE30-0UB0	CONVERTER
G120X (400V,IP20,18,5kW,UF,PN,IOP-2,3C2)	6SL3220-3YE30-0UF0	CONVERTER
G120X (400V,IP20,18,5kW,UF,DP,IOP-2,3C2)	6SL3220-3YE30-0UP0	CONVERTER
G120X (400V,IP20,18,5kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE30-1AB0	CONVERTER
G120X (400V,IP20,18,5kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE30-1AF0	CONVERTER
G120X (400V,IP20,18,5kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE30-1AP0	CONVERTER
G120X (400V,IP20,18,5kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE30-1UB0	CONVERTER
G120X (400V,IP20,18,5kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE30-1UF0	CONVERTER
G120X (400V,IP20,18,5kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE30-1UP0	CONVERTER
G120X (400V,IP20,22kW,C2,USS,IOP-2,3C2)	6SL3220-3YE32-0AB0	CONVERTER
G120X (400V,IP20,22kW,C2,PN,IOP-2,3C2)	6SL3220-3YE32-0AF0	CONVERTER

G120X (400V,IP20,22kW,C2,DP,IOP-2,3C2)	6SL3220-3YE32-0AP0	CONVERTER
G120X (400V,IP20,22kW,UF,USS,IOP-2,3C2)	6SL3220-3YE32-0UB0	CONVERTER
G120X (400V,IP20,22kW,UF,PN,IOP-2,3C2)	6SL3220-3YE32-0UF0	CONVERTER
G120X (400V,IP20,22kW,UF,DP,IOP-2,3C2)	6SL3220-3YE32-0UP0	CONVERTER
G120X (400V,IP20,22kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE32-1AB0	CONVERTER
G120X (400V,IP20,22kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE32-1AF0	CONVERTER
G120X (400V,IP20,22kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE32-1AP0	CONVERTER
G120X (400V,IP20,22kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE32-1UB0	CONVERTER
G120X (400V,IP20,22kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE32-1UF0	CONVERTER
G120X (400V,IP20,22kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE32-1UP0	CONVERTER
G120X (400V,IP20,30kW,C2,USS,IOP-2,3C2)	6SL3220-3YE34-0AB0	CONVERTER
G120X (400V,IP20,30kW,C2,PN,IOP-2,3C2)	6SL3220-3YE34-0AF0	CONVERTER
G120X (400V,IP20,30kW,C2,DP,IOP-2,3C2)	6SL3220-3YE34-0AP0	CONVERTER
G120X (400V,IP20,30kW,UF,USS,IOP-2,3C2)	6SL3220-3YE34-0UB0	CONVERTER
G120X (400V,IP20,30kW,UF,PN,IOP-2,3C2)	6SL3220-3YE34-0UF0	CONVERTER
G120X (400V,IP20,30kW,UF,DP,IOP-2,3C2)	6SL3220-3YE34-0UP0	CONVERTER
G120X (400V,IP20,30kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE34-1AB0	CONVERTER
G120X (400V,IP20,30kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE34-1AF0	CONVERTER
G120X (400V,IP20,30kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE34-1AP0	CONVERTER
G120X (400V,IP20,30kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE34-1UB0	CONVERTER
G120X (400V,IP20,30kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE34-1UF0	CONVERTER
G120X (400V,IP20,30kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE34-1UP0	CONVERTER
G120X (400V,IP20,37kW,C2,USS,IOP-2,3C2)	6SL3220-3YE36-0AB0	CONVERTER
G120X (400V,IP20,37kW,C2,PN,IOP-2,3C2)	6SL3220-3YE36-0AF0	CONVERTER
G120X (400V,IP20,37kW,C2,DP,IOP-2,3C2)	6SL3220-3YE36-0AP0	CONVERTER
G120X (400V,IP20,37kW,UF,USS,IOP-2,3C2)	6SL3220-3YE36-0UB0	CONVERTER
G120X (400V,IP20,37kW,UF,PN,IOP-2,3C2)	6SL3220-3YE36-0UF0	CONVERTER
G120X (400V,IP20,37kW,UF,DP,IOP-2,3C2)	6SL3220-3YE36-0UP0	CONVERTER
G120X (400V,IP20,37kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE36-1AB0	CONVERTER
G120X (400V,IP20,37kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE36-1AF0	CONVERTER
G120X (400V,IP20,37kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE36-1AP0	CONVERTER
G120X (400V,IP20,37kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE36-1UB0	CONVERTER
G120X (400V,IP20,37kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE36-1UF0	CONVERTER
G120X (400V,IP20,37kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE36-1UP0	CONVERTER
G120X (400V,IP20,45kW,C2,USS,IOP-2,3C2)	6SL3220-3YE38-0AB0	CONVERTER
G120X (400V,IP20,45kW,C2,PN,IOP-2,3C2)	6SL3220-3YE38-0AF0	CONVERTER
G120X (400V,IP20,45kW,C2,DP,IOP-2,3C2)	6SL3220-3YE38-0AP0	CONVERTER
G120X (400V,IP20,45kW,UF,USS,IOP-2,3C2)	6SL3220-3YE38-0UB0	CONVERTER
G120X (400V,IP20,45kW,UF,PN,IOP-2,3C2)	6SL3220-3YE38-0UF0	CONVERTER
G120X (400V,IP20,45kW,UF,DP,IOP-2,3C2)	6SL3220-3YE38-0UP0	CONVERTER
G120X (400V,IP20,45kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE38-1AB0	CONVERTER
G120X (400V,IP20,45kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE38-1AF0	CONVERTER
G120X (400V,IP20,45kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE38-1AP0	CONVERTER
G120X (400V,IP20,45kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE38-1UB0	CONVERTER

G120X (400V,IP20,45kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE38-1UF0	CONVERTER
G120X (400V,IP20,45kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE38-1UP0	CONVERTER
G120X (400V,IP20,55kW,C2,USS,IOP-2,3C2)	6SL3220-3YE40-0AB0	CONVERTER
G120X (400V,IP20,55kW,C2,PN,IOP-2,3C2)	6SL3220-3YE40-0AF0	CONVERTER
G120X (400V,IP20,55kW,C2,DP,IOP-2,3C2)	6SL3220-3YE40-0AP0	CONVERTER
G120X (400V,IP20,55kW,UF,USS,IOP-2,3C2)	6SL3220-3YE40-0UB0	CONVERTER
G120X (400V,IP20,55kW,UF,PN,IOP-2,3C2)	6SL3220-3YE40-0UF0	CONVERTER
G120X (400V,IP20,55kW,UF,DP,IOP-2,3C2)	6SL3220-3YE40-0UP0	CONVERTER
G120X (400V,IP20,55kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE40-1AB0	CONVERTER
G120X (400V,IP20,55kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE40-1AF0	CONVERTER
G120X (400V,IP20,55kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE40-1AP0	CONVERTER
G120X (400V,IP20,55kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE40-1UB0	CONVERTER
G120X (400V,IP20,55kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE40-1UF0	CONVERTER
G120X (400V,IP20,55kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE40-1UP0	CONVERTER
G120X (400V,IP20,75kW,C2,USS,IOP-2,3C2)	6SL3220-3YE42-0AB0	CONVERTER
G120X (400V,IP20,75kW,C2,PN,IOP-2,3C2)	6SL3220-3YE42-0AF0	CONVERTER
G120X (400V,IP20,75kW,C2,DP,IOP-2,3C2)	6SL3220-3YE42-0AP0	CONVERTER
G120X (400V,IP20,75kW,UF,USS,IOP-2,3C2)	6SL3220-3YE42-0UB0	CONVERTER
G120X (400V,IP20,75kW,UF,PN,IOP-2,3C2)	6SL3220-3YE42-0UF0	CONVERTER
G120X (400V,IP20,75kW,UF,DP,IOP-2,3C2)	6SL3220-3YE42-0UP0	CONVERTER
G120X (400V,IP20,75kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE42-1AB0	CONVERTER
G120X (400V,IP20,75kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE42-1AF0	CONVERTER
G120X (400V,IP20,75kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE42-1AP0	CONVERTER
G120X (400V,IP20,75kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE42-1UB0	CONVERTER
G120X (400V,IP20,75kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE42-1UF0	CONVERTER
G120X (400V,IP20,75kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE42-1UP0	CONVERTER
G120X (400V,IP20,90kW,C2,USS,IOP-2,3C2)	6SL3220-3YE44-0AB0	CONVERTER
G120X (400V,IP20,90kW,C2,PN,IOP-2,3C2)	6SL3220-3YE44-0AF0	CONVERTER
G120X (400V,IP20,90kW,C2,DP,IOP-2,3C2)	6SL3220-3YE44-0AP0	CONVERTER
G120X (400V,IP20,90kW,UF,USS,IOP-2,3C2)	6SL3220-3YE44-0UB0	CONVERTER
G120X (400V,IP20,90kW,UF,PN,IOP-2,3C2)	6SL3220-3YE44-0UF0	CONVERTER
G120X (400V,IP20,90kW,UF,DP,IOP-2,3C2)	6SL3220-3YE44-0UP0	CONVERTER
G120X (400V,IP20,90kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE44-1AB0	CONVERTER
G120X (400V,IP20,90kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE44-1AF0	CONVERTER
G120X (400V,IP20,90kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE44-1AP0	CONVERTER
G120X (400V,IP20,90kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE44-1UB0	CONVERTER
G120X (400V,IP20,90kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE44-1UF0	CONVERTER
G120X (400V,IP20,90kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE44-1UP0	CONVERTER
G120X (400V,IP20,110kW,C2,USS,IOP-2,3C2)	6SL3220-3YE46-0AB0	CONVERTER
G120X (400V,IP20,110kW,C2,PN,IOP-2,3C2)	6SL3220-3YE46-0AF0	CONVERTER
G120X (400V,IP20,110kW,C2,DP,IOP-2,3C2)	6SL3220-3YE46-0AP0	CONVERTER
G120X (400V,IP20,110kW,UF,USS,IOP-2,3C2)	6SL3220-3YE46-0UB0	CONVERTER
G120X (400V,IP20,110kW,UF,PN,IOP-2,3C2)	6SL3220-3YE46-0UF0	CONVERTER
G120X (400V,IP20,110kW,UF,DP,IOP-2,3C2)	6SL3220-3YE46-0UP0	CONVERTER

G120X (400V,IP20,110kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE46-1AB0	CONVERTER
G120X (400V,IP20,110kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE46-1AF0	CONVERTER
G120X (400V,IP20,110kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE46-1AP0	CONVERTER
G120X (400V,IP20,110kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE46-1UB0	CONVERTER
G120X (400V,IP20,110kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE46-1UF0	CONVERTER
G120X (400V,IP20,110kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE46-1UP0	CONVERTER
G120X (400V,IP20,132kW,C2,USS,IOP-2,3C2)	6SL3220-3YE48-0AB0	CONVERTER
G120X (400V,IP20,132kW,C2,PN,IOP-2,3C2)	6SL3220-3YE48-0AF0	CONVERTER
G120X (400V,IP20,132kW,C2,DP,IOP-2,3C2)	6SL3220-3YE48-0AP0	CONVERTER
G120X (400V,IP20,132kW,UF,USS,IOP-2,3C2)	6SL3220-3YE48-0UB0	CONVERTER
G120X (400V,IP20,132kW,UF,PN,IOP-2,3C2)	6SL3220-3YE48-0UF0	CONVERTER
G120X (400V,IP20,132kW,UF,DP,IOP-2,3C2)	6SL3220-3YE48-0UP0	CONVERTER
G120X (400V,IP20,132kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE48-1AB0	CONVERTER
G120X (400V,IP20,132kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE48-1AF0	CONVERTER
G120X (400V,IP20,132kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE48-1AP0	CONVERTER
G120X (400V,IP20,132kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YE48-1UB0	CONVERTER
G120X (400V,IP20,132kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YE48-1UF0	CONVERTER
G120X (400V,IP20,132kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YE48-1UP0	CONVERTER
G120X (400V,IP20,160kW,C2,USS,IOP-2,3C2)	6SL3220-3YE50-0AB0	CONVERTER
G120X (400V,IP20,160kW,C2,PN,IOP-2,3C2)	6SL3220-3YE50-0AF0	CONVERTER
G120X (400V,IP20,160kW,C2,DP,IOP-2,3C2)	6SL3220-3YE50-0AP0	CONVERTER
G120X (400V,IP20,160kW,C3,USS,IOP-2,3C2)	6SL3220-3YE50-0CB0	CONVERTER
G120X (400V,IP20,160kW,C3,PN,IOP-2,3C2)	6SL3220-3YE50-0CF0	CONVERTER
G120X (400V,IP20,160kW,C3,DP,IOP-2,3C2)	6SL3220-3YE50-0CP0	CONVERTER
G120X (400V,IP20,160kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE50-1AB0	CONVERTER
G120X (400V,IP20,160kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE50-1AF0	CONVERTER
G120X (400V,IP20,160kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE50-1AP0	CONVERTER
G120X (400V,IP20,160kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YE50-1CB0	CONVERTER
G120X (400V,IP20,160kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YE50-1CF0	CONVERTER
G120X (400V,IP20,160kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YE50-1CP0	CONVERTER
G120X (400V,IP20,200kW,C2,USS,IOP-2,3C2)	6SL3220-3YE52-0AB0	CONVERTER
G120X (400V,IP20,200kW,C2,PN,IOP-2,3C2)	6SL3220-3YE52-0AF0	CONVERTER
G120X (400V,IP20,200kW,C2,DP,IOP-2,3C2)	6SL3220-3YE52-0AP0	CONVERTER
G120X (400V,IP20,200kW,C3,USS,IOP-2,3C2)	6SL3220-3YE52-0CB0	CONVERTER
G120X (400V,IP20,200kW,C3,PN,IOP-2,3C2)	6SL3220-3YE52-0CF0	CONVERTER
G120X (400V,IP20,200kW,C3,DP,IOP-2,3C2)	6SL3220-3YE52-0CP0	CONVERTER
G120X (400V,IP20,200kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE52-1AB0	CONVERTER
G120X (400V,IP20,200kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE52-1AF0	CONVERTER
G120X (400V,IP20,200kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE52-1AP0	CONVERTER
G120X (400V,IP20,200kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YE52-1CB0	CONVERTER
G120X (400V,IP20,200kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YE52-1CF0	CONVERTER
G120X (400V,IP20,200kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YE52-1CP0	CONVERTER
G120X (400V,IP20,250kW,C2,USS,IOP-2,3C2)	6SL3220-3YE54-0AB0	CONVERTER
G120X (400V,IP20,250kW,C2,PN,IOP-2,3C2)	6SL3220-3YE54-0AF0	CONVERTER

G120X (400V,IP20,250kW,C2,DP,IOP-2,3C2)	6SL3220-3YE54-0AP0	CONVERTER
G120X (400V,IP20,250kW,C3,USS,IOP-2,3C2)	6SL3220-3YE54-0CB0	CONVERTER
G120X (400V,IP20,250kW,C3,PN,IOP-2,3C2)	6SL3220-3YE54-0CF0	CONVERTER
G120X (400V,IP20,250kW,C3,DP,IOP-2,3C2)	6SL3220-3YE54-0CP0	CONVERTER
G120X (400V,IP20,250kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YE54-1AB0	CONVERTER
G120X (400V,IP20,250kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YE54-1AF0	CONVERTER
G120X (400V,IP20,250kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YE54-1AP0	CONVERTER
G120X (400V,IP20,250kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YE54-1CB0	CONVERTER
G120X (400V,IP20,250kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YE54-1CF0	CONVERTER
G120X (400V,IP20,250kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YE54-1CP0	CONVERTER
G120X (400V,IP20,315kW,C3,USS,IOP-2,3C2)	6SL3220-3YE56-0CB0	CONVERTER
G120X (400V,IP20,315kW,C3,PN,IOP-2,3C2)	6SL3220-3YE56-0CF0	CONVERTER
G120X (400V,IP20,315kW,C3,DP,IOP-2,3C2)	6SL3220-3YE56-0CP0	CONVERTER
G120X (400V,IP20,315kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YE56-1CB0	CONVERTER
G120X (400V,IP20,315kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YE56-1CF0	CONVERTER
G120X (400V,IP20,315kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YE56-1CP0	CONVERTER
G120X (400V,IP20,355kW,C3,USS,IOP-2,3C2)	6SL3220-3YE58-0CB0	CONVERTER
G120X (400V,IP20,355kW,C3,PN,IOP-2,3C2)	6SL3220-3YE58-0CF0	CONVERTER
G120X (400V,IP20,355kW,C3,DP,IOP-2,3C2)	6SL3220-3YE58-0CP0	CONVERTER
G120X (400V,IP20,355kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YE58-1CB0	CONVERTER
G120X (400V,IP20,355kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YE58-1CF0	CONVERTER
G120X (400V,IP20,355kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YE58-1CP0	CONVERTER
G120X (400V,IP20,400kW,C3,USS,IOP-2,3C2)	6SL3220-3YE60-0CB0	CONVERTER
G120X (400V,IP20,400kW,C3,PN,IOP-2,3C2)	6SL3220-3YE60-0CF0	CONVERTER
G120X (400V,IP20,400kW,C3,DP,IOP-2,3C2)	6SL3220-3YE60-0CP0	CONVERTER
G120X (400V,IP20,400kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YE60-1CB0	CONVERTER
G120X (400V,IP20,400kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YE60-1CF0	CONVERTER
G120X (400V,IP20,400kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YE60-1CP0	CONVERTER
G120X (400V,IP20,450kW,C3,USS,IOP-2,3C2)	6SL3220-3YE62-0CB0	CONVERTER
G120X (400V,IP20,450kW,C3,PN,IOP-2,3C2)	6SL3220-3YE62-0CF0	CONVERTER
G120X (400V,IP20,450kW,C3,DP,IOP-2,3C2)	6SL3220-3YE62-0CP0	CONVERTER
G120X (400V,IP20,450kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YE62-1CB0	CONVERTER
G120X (400V,IP20,450kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YE62-1CF0	CONVERTER
G120X (400V,IP20,450kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YE62-1CP0	CONVERTER
G120X (400V,IP20,500kW,C3,USS,IOP-2,3C2)	6SL3220-3YE64-0CB0	CONVERTER
G120X (400V,IP20,500kW,C3,PN,IOP-2,3C2)	6SL3220-3YE64-0CF0	CONVERTER
G120X (400V,IP20,500kW,C3,DP,IOP-2,3C2)	6SL3220-3YE64-0CP0	CONVERTER
G120X (400V,IP20,500kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YE64-1CB0	CONVERTER
G120X (400V,IP20,500kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YE64-1CF0	CONVERTER
G120X (400V,IP20,500kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YE64-1CP0	CONVERTER
G120X (400V,IP20,560kW,C3,USS,IOP-2,3C2)	6SL3220-3YE66-0CB0	CONVERTER
G120X (400V,IP20,560kW,C3,PN,IOP-2,3C2)	6SL3220-3YE66-0CF0	CONVERTER
G120X (400V,IP20,560kW,C3,DP,IOP-2,3C2)	6SL3220-3YE66-0CP0	CONVERTER
G120X (400V,IP20,560kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YE66-1CB0	CONVERTER

G120X (400V,IP20,560kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YE66-1CF0	CONVERTER
G120X (400V,IP20,560kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YE66-1CP0	CONVERTER
G120X (690V,IP20,3kW,C2,USS,IOP-2,3C2)	6SL3220-3YH18-0AB0	CONVERTER
G120X (690V,IP20,3kW,C2,PN,IOP-2,3C2)	6SL3220-3YH18-0AF0	CONVERTER
G120X (690V,IP20,3kW,C2,DP,IOP-2,3C2)	6SL3220-3YH18-0AP0	CONVERTER
G120X (690V,IP20,3kW,UF,USS,IOP-2,3C2)	6SL3220-3YH18-0UB0	CONVERTER
G120X (690V,IP20,3kW,UF,PN,IOP-2,3C2)	6SL3220-3YH18-0UF0	CONVERTER
G120X (690V,IP20,3kW,UF,DP,IOP-2,3C2)	6SL3220-3YH18-0UP0	CONVERTER
G120X (690V,IP20,3kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YH18-1AB0	CONVERTER
G120X (690V,IP20,3kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YH18-1AF0	CONVERTER
G120X (690V,IP20,3kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YH18-1AP0	CONVERTER
G120X (690V,IP20,3kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH18-1UB0	CONVERTER
G120X (690V,IP20,3kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH18-1UF0	CONVERTER
G120X (690V,IP20,3kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH18-1UP0	CONVERTER
G120X (690V,IP20,4kW,C2,USS,IOP-2,3C2)	6SL3220-3YH20-0AB0	CONVERTER
G120X (690V,IP20,4kW,C2,PN,IOP-2,3C2)	6SL3220-3YH20-0AF0	CONVERTER
G120X (690V,IP20,4kW,C2,DP,IOP-2,3C2)	6SL3220-3YH20-0AP0	CONVERTER
G120X (690V,IP20,4kW,UF,USS,IOP-2,3C2)	6SL3220-3YH20-0UB0	CONVERTER
G120X (690V,IP20,4kW,UF,PN,IOP-2,3C2)	6SL3220-3YH20-0UF0	CONVERTER
G120X (690V,IP20,4kW,UF,DP,IOP-2,3C2)	6SL3220-3YH20-0UP0	CONVERTER
G120X (690V,IP20,4kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YH20-1AB0	CONVERTER
G120X (690V,IP20,4kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YH20-1AF0	CONVERTER
G120X (690V,IP20,4kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YH20-1AP0	CONVERTER
G120X (690V,IP20,4kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH20-1UB0	CONVERTER
G120X (690V,IP20,4kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH20-1UF0	CONVERTER
G120X (690V,IP20,4kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH20-1UP0	CONVERTER
G120X (690V,IP20,5.5kW,C2,USS,IOP-2,3C2)	6SL3220-3YH22-0AB0	CONVERTER
G120X (690V,IP20,5.5kW,C2,PN,IOP-2,3C2)	6SL3220-3YH22-0AF0	CONVERTER
G120X (690V,IP20,5.5kW,C2,DP,IOP-2,3C2)	6SL3220-3YH22-0AP0	CONVERTER
G120X (690V,IP20,5.5kW,UF,USS,IOP-2,3C2)	6SL3220-3YH22-0UB0	CONVERTER
G120X (690V,IP20,5.5kW,UF,PN,IOP-2,3C2)	6SL3220-3YH22-0UF0	CONVERTER
G120X (690V,IP20,5.5kW,UF,DP,IOP-2,3C2)	6SL3220-3YH22-0UP0	CONVERTER
G120X (690V,IP20,5.5kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YH22-1AB0	CONVERTER
G120X (690V,IP20,5.5kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YH22-1AF0	CONVERTER
G120X (690V,IP20,5.5kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YH22-1AP0	CONVERTER
G120X (690V,IP20,5.5kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH22-1UB0	CONVERTER
G120X (690V,IP20,5.5kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH22-1UF0	CONVERTER
G120X (690V,IP20,5.5kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH22-1UP0	CONVERTER
G120X (690V,IP20,7.5kW,C2,USS,IOP-2,3C2)	6SL3220-3YH24-0AB0	CONVERTER
G120X (690V,IP20,7.5kW,C2,PN,IOP-2,3C2)	6SL3220-3YH24-0AF0	CONVERTER
G120X (690V,IP20,7.5kW,C2,DP,IOP-2,3C2)	6SL3220-3YH24-0AP0	CONVERTER
G120X (690V,IP20,7.5kW,UF,USS,IOP-2,3C2)	6SL3220-3YH24-0UB0	CONVERTER
G120X (690V,IP20,7.5kW,UF,PN,IOP-2,3C2)	6SL3220-3YH24-0UF0	CONVERTER
G120X (690V,IP20,7.5kW,UF,DP,IOP-2,3C2)	6SL3220-3YH24-0UP0	CONVERTER

G120X (690V,IP20,7.5kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YH24-1AB0	CONVERTER
G120X (690V,IP20,7.5kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YH24-1AF0	CONVERTER
G120X (690V,IP20,7.5kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YH24-1AP0	CONVERTER
G120X (690V,IP20,7.5kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH24-1UB0	CONVERTER
G120X (690V,IP20,7.5kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH24-1UF0	CONVERTER
G120X (690V,IP20,7.5kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH24-1UP0	CONVERTER
G120X (690V,IP20,11kW,C2,USS,IOP-2,3C2)	6SL3220-3YH26-0AB0	CONVERTER
G120X (690V,IP20,11kW,C2,PN,IOP-2,3C2)	6SL3220-3YH26-0AF0	CONVERTER
G120X (690V,IP20,11kW,C2,DP,IOP-2,3C2)	6SL3220-3YH26-0AP0	CONVERTER
G120X (690V,IP20,11kW,UF,USS,IOP-2,3C2)	6SL3220-3YH26-0UB0	CONVERTER
G120X (690V,IP20,11kW,UF,PN,IOP-2,3C2)	6SL3220-3YH26-0UF0	CONVERTER
G120X (690V,IP20,11kW,UF,DP,IOP-2,3C2)	6SL3220-3YH26-0UP0	CONVERTER
G120X (690V,IP20,11kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YH26-1AB0	CONVERTER
G120X (690V,IP20,11kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YH26-1AF0	CONVERTER
G120X (690V,IP20,11kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YH26-1AP0	CONVERTER
G120X (690V,IP20,11kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH26-1UB0	CONVERTER
G120X (690V,IP20,11kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH26-1UF0	CONVERTER
G120X (690V,IP20,11kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH26-1UP0	CONVERTER
G120X (690V,IP20,15kW,C2,USS,IOP-2,3C2)	6SL3220-3YH28-0AB0	CONVERTER
G120X (690V,IP20,15kW,C2,PN,IOP-2,3C2)	6SL3220-3YH28-0AF0	CONVERTER
G120X (690V,IP20,15kW,C2,DP,IOP-2,3C2)	6SL3220-3YH28-0AP0	CONVERTER
G120X (690V,IP20,15kW,UF,USS,IOP-2,3C2)	6SL3220-3YH28-0UB0	CONVERTER
G120X (690V,IP20,15kW,UF,PN,IOP-2,3C2)	6SL3220-3YH28-0UF0	CONVERTER
G120X (690V,IP20,15kW,UF,DP,IOP-2,3C2)	6SL3220-3YH28-0UP0	CONVERTER
G120X (690V,IP20,15kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YH28-1AB0	CONVERTER
G120X (690V,IP20,15kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YH28-1AF0	CONVERTER
G120X (690V,IP20,15kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YH28-1AP0	CONVERTER
G120X (690V,IP20,15kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH28-1UB0	CONVERTER
G120X (690V,IP20,15kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH28-1UF0	CONVERTER
G120X (690V,IP20,15kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH28-1UP0	CONVERTER
G120X (690V,IP20,18,5kW,C2,USS,IOP-2,3C2)	6SL3220-3YH30-0AB0	CONVERTER
G120X (690V,IP20,18,5kW,C2,PN,IOP-2,3C2)	6SL3220-3YH30-0AF0	CONVERTER
G120X (690V,IP20,18,5kW,C2,DP,IOP-2,3C2)	6SL3220-3YH30-0AP0	CONVERTER
G120X (690V,IP20,18,5kW,UF,USS,IOP-2,3C2)	6SL3220-3YH30-0UB0	CONVERTER
G120X (690V,IP20,18,5kW,UF,PN,IOP-2,3C2)	6SL3220-3YH30-0UF0	CONVERTER
G120X (690V,IP20,18,5kW,UF,DP,IOP-2,3C2)	6SL3220-3YH30-0UP0	CONVERTER
G120X (690V,IP20,18,5kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YH30-1AB0	CONVERTER
G120X (690V,IP20,18,5kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YH30-1AF0	CONVERTER
G120X (690V,IP20,18,5kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YH30-1AP0	CONVERTER
G120X (690V,IP20,18,5kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH30-1UB0	CONVERTER
G120X (690V,IP20,18,5kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH30-1UF0	CONVERTER
G120X (690V,IP20,18,5kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH30-1UP0	CONVERTER
G120X (690V,IP20,22kW,C2,USS,IOP-2,3C2)	6SL3220-3YH32-0AB0	CONVERTER
G120X (690V,IP20,22kW,C2,PN,IOP-2,3C2)	6SL3220-3YH32-0AF0	CONVERTER

G120X (690V,IP20,22kW,C2,DP,IOP-2,3C2)	6SL3220-3YH32-0AP0	CONVERTER
G120X (690V,IP20,22kW,UF,USS,IOP-2,3C2)	6SL3220-3YH32-0UB0	CONVERTER
G120X (690V,IP20,22kW,UF,PN,IOP-2,3C2)	6SL3220-3YH32-0UF0	CONVERTER
G120X (690V,IP20,22kW,UF,DP,IOP-2,3C2)	6SL3220-3YH32-0UP0	CONVERTER
G120X (690V,IP20,22kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YH32-1AB0	CONVERTER
G120X (690V,IP20,22kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YH32-1AF0	CONVERTER
G120X (690V,IP20,22kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YH32-1AP0	CONVERTER
G120X (690V,IP20,22kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH32-1UB0	CONVERTER
G120X (690V,IP20,22kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH32-1UF0	CONVERTER
G120X (690V,IP20,22kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH32-1UP0	CONVERTER
G120X (690V,IP20,30kW,C2,USS,IOP-2,3C2)	6SL3220-3YH34-0AB0	CONVERTER
G120X (690V,IP20,30kW,C2,PN,IOP-2,3C2)	6SL3220-3YH34-0AF0	CONVERTER
G120X (690V,IP20,30kW,C2,DP,IOP-2,3C2)	6SL3220-3YH34-0AP0	CONVERTER
G120X (690V,IP20,30kW,UF,USS,IOP-2,3C2)	6SL3220-3YH34-0UB0	CONVERTER
G120X (690V,IP20,30kW,UF,PN,IOP-2,3C2)	6SL3220-3YH34-0UF0	CONVERTER
G120X (690V,IP20,30kW,UF,DP,IOP-2,3C2)	6SL3220-3YH34-0UP0	CONVERTER
G120X (690V,IP20,30kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YH34-1AB0	CONVERTER
G120X (690V,IP20,30kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YH34-1AF0	CONVERTER
G120X (690V,IP20,30kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YH34-1AP0	CONVERTER
G120X (690V,IP20,30kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH34-1UB0	CONVERTER
G120X (690V,IP20,30kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH34-1UF0	CONVERTER
G120X (690V,IP20,30kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH34-1UP0	CONVERTER
G120X (690V,IP20,37kW,C2,USS,IOP-2,3C2)	6SL3220-3YH36-0AB0	CONVERTER
G120X (690V,IP20,37kW,C2,PN,IOP-2,3C2)	6SL3220-3YH36-0AF0	CONVERTER
G120X (690V,IP20,37kW,C2,DP,IOP-2,3C2)	6SL3220-3YH36-0AP0	CONVERTER
G120X (690V,IP20,37kW,UF,USS,IOP-2,3C2)	6SL3220-3YH36-0UB0	CONVERTER
G120X (690V,IP20,37kW,UF,PN,IOP-2,3C2)	6SL3220-3YH36-0UF0	CONVERTER
G120X (690V,IP20,37kW,UF,DP,IOP-2,3C2)	6SL3220-3YH36-0UP0	CONVERTER
G120X (690V,IP20,37kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YH36-1AB0	CONVERTER
G120X (690V,IP20,37kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YH36-1AF0	CONVERTER
G120X (690V,IP20,37kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YH36-1AP0	CONVERTER
G120X (690V,IP20,37kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH36-1UB0	CONVERTER
G120X (690V,IP20,37kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH36-1UF0	CONVERTER
G120X (690V,IP20,37kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH36-1UP0	CONVERTER
G120X (690V,IP20,45kW,C2,USS,IOP-2,3C2)	6SL3220-3YH38-0AB0	CONVERTER
G120X (690V,IP20,45kW,C2,PN,IOP-2,3C2)	6SL3220-3YH38-0AF0	CONVERTER
G120X (690V,IP20,45kW,C2,DP,IOP-2,3C2)	6SL3220-3YH38-0AP0	CONVERTER
G120X (690V,IP20,45kW,UF,USS,IOP-2,3C2)	6SL3220-3YH38-0UB0	CONVERTER
G120X (690V,IP20,45kW,UF,PN,IOP-2,3C2)	6SL3220-3YH38-0UF0	CONVERTER
G120X (690V,IP20,45kW,UF,DP,IOP-2,3C2)	6SL3220-3YH38-0UP0	CONVERTER
G120X (690V,IP20,45kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YH38-1AB0	CONVERTER
G120X (690V,IP20,45kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YH38-1AF0	CONVERTER
G120X (690V,IP20,45kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YH38-1AP0	CONVERTER
G120X (690V,IP20,45kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH38-1UB0	CONVERTER

G120X (690V,IP20,45kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH38-1UF0	CONVERTER
G120X (690V,IP20,45kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH38-1UP0	CONVERTER
G120X (690V,IP20,55kW,C2,USS,IOP-2,3C2)	6SL3220-3YH40-0AB0	CONVERTER
G120X (690V,IP20,55kW,C2,PN,IOP-2,3C2)	6SL3220-3YH40-0AF0	CONVERTER
G120X (690V,IP20,55kW,C2,DP,IOP-2,3C2)	6SL3220-3YH40-0AP0	CONVERTER
G120X (690V,IP20,55kW,UF,USS,IOP-2,3C2)	6SL3220-3YH40-0UB0	CONVERTER
G120X (690V,IP20,55kW,UF,PN,IOP-2,3C2)	6SL3220-3YH40-0UF0	CONVERTER
G120X (690V,IP20,55kW,UF,DP,IOP-2,3C2)	6SL3220-3YH40-0UP0	CONVERTER
G120X (690V,IP20,55kW,C2,USS,IOP-2,3C2,IO)	6SL3220-3YH40-1AB0	CONVERTER
G120X (690V,IP20,55kW,C2,PN,IOP-2,3C2,IO)	6SL3220-3YH40-1AF0	CONVERTER
G120X (690V,IP20,55kW,C2,DP,IOP-2,3C2,IO)	6SL3220-3YH40-1AP0	CONVERTER
G120X (690V,IP20,55kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH40-1UB0	CONVERTER
G120X (690V,IP20,55kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH40-1UF0	CONVERTER
G120X (690V,IP20,55kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH40-1UP0	CONVERTER
G120X (690V,IP20,75kW,C3,USS,IOP-2,3C2)	6SL3220-3YH42-0CB0	CONVERTER
G120X (690V,IP20,75kW,C3,PN,IOP-2,3C2)	6SL3220-3YH42-0CF0	CONVERTER
G120X (690V,IP20,75kW,C3,DP,IOP-2,3C2)	6SL3220-3YH42-0CP0	CONVERTER
G120X (690V,IP20,75kW,UF,USS,IOP-2,3C2)	6SL3220-3YH42-0UB0	CONVERTER
G120X (690V,IP20,75kW,UF,PN,IOP-2,3C2)	6SL3220-3YH42-0UF0	CONVERTER
G120X (690V,IP20,75kW,UF,DP,IOP-2,3C2)	6SL3220-3YH42-0UP0	CONVERTER
G120X (690V,IP20,75kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YH42-1CB0	CONVERTER
G120X (690V,IP20,75kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YH42-1CF0	CONVERTER
G120X (690V,IP20,75kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YH42-1CP0	CONVERTER
G120X (690V,IP20,75kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH42-1UB0	CONVERTER
G120X (690V,IP20,75kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH42-1UF0	CONVERTER
G120X (690V,IP20,75kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH42-1UP0	CONVERTER
G120X (690V,IP20,90kW,C3,USS,IOP-2,3C2)	6SL3220-3YH44-0CB0	CONVERTER
G120X (690V,IP20,90kW,C3,PN,IOP-2,3C2)	6SL3220-3YH44-0CF0	CONVERTER
G120X (690V,IP20,90kW,C3,DP,IOP-2,3C2)	6SL3220-3YH44-0CP0	CONVERTER
G120X (690V,IP20,90kW,UF,USS,IOP-2,3C2)	6SL3220-3YH44-0UB0	CONVERTER
G120X (690V,IP20,90kW,UF,PN,IOP-2,3C2)	6SL3220-3YH44-0UF0	CONVERTER
G120X (690V,IP20,90kW,UF,DP,IOP-2,3C2)	6SL3220-3YH44-0UP0	CONVERTER
G120X (690V,IP20,90kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YH44-1CB0	CONVERTER
G120X (690V,IP20,90kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YH44-1CF0	CONVERTER
G120X (690V,IP20,90kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YH44-1CP0	CONVERTER
G120X (690V,IP20,90kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH44-1UB0	CONVERTER
G120X (690V,IP20,90kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH44-1UF0	CONVERTER
G120X (690V,IP20,90kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH44-1UP0	CONVERTER
G120X (690V,IP20,110kW,C3,USS,IOP-2,3C2)	6SL3220-3YH46-0CB0	CONVERTER
G120X (690V,IP20,110kW,C3,PN,IOP-2,3C2)	6SL3220-3YH46-0CF0	CONVERTER
G120X (690V,IP20,110kW,C3,DP,IOP-2,3C2)	6SL3220-3YH46-0CP0	CONVERTER
G120X (690V,IP20,110kW,UF,USS,IOP-2,3C2)	6SL3220-3YH46-0UB0	CONVERTER
G120X (690V,IP20,110kW,UF,PN,IOP-2,3C2)	6SL3220-3YH46-0UF0	CONVERTER
G120X (690V,IP20,110kW,UF,DP,IOP-2,3C2)	6SL3220-3YH46-0UP0	CONVERTER

G120X (690V,IP20,110kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YH46-1CB0	CONVERTER
G120X (690V,IP20,110kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YH46-1CF0	CONVERTER
G120X (690V,IP20,110kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YH46-1CP0	CONVERTER
G120X (690V,IP20,110kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH46-1UB0	CONVERTER
G120X (690V,IP20,110kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH46-1UF0	CONVERTER
G120X (690V,IP20,110kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH46-1UP0	CONVERTER
G120X (690V,IP20,132kW,C3,USS,IOP-2,3C2)	6SL3220-3YH48-0CB0	CONVERTER
G120X (690V,IP20,132kW,C3,PN,IOP-2,3C2)	6SL3220-3YH48-0CF0	CONVERTER
G120X (690V,IP20,132kW,C3,DP,IOP-2,3C2)	6SL3220-3YH48-0CP0	CONVERTER
G120X (690V,IP20,132kW,UF,USS,IOP-2,3C2)	6SL3220-3YH48-0UB0	CONVERTER
G120X (690V,IP20,132kW,UF,PN,IOP-2,3C2)	6SL3220-3YH48-0UF0	CONVERTER
G120X (690V,IP20,132kW,UF,DP,IOP-2,3C2)	6SL3220-3YH48-0UP0	CONVERTER
G120X (690V,IP20,132kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YH48-1CB0	CONVERTER
G120X (690V,IP20,132kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YH48-1CF0	CONVERTER
G120X (690V,IP20,132kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YH48-1CP0	CONVERTER
G120X (690V,IP20,132kW,UF,USS,IOP-2,3C2,IO)	6SL3220-3YH48-1UB0	CONVERTER
G120X (690V,IP20,132kW,UF,PN,IOP-2,3C2,IO)	6SL3220-3YH48-1UF0	CONVERTER
G120X (690V,IP20,132kW,UF,DP,IOP-2,3C2,IO)	6SL3220-3YH48-1UP0	CONVERTER
G120X (690V,IP20,160kW,C3,USS,IOP-2,3C2)	6SL3220-3YH50-0CB0	CONVERTER
G120X (690V,IP20,160kW,C3,PN,IOP-2,3C2)	6SL3220-3YH50-0CF0	CONVERTER
G120X (690V,IP20,160kW,C3,DP,IOP-2,3C2)	6SL3220-3YH50-0CP0	CONVERTER
G120X (690V,IP20,160kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YH50-1CB0	CONVERTER
G120X (690V,IP20,160kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YH50-1CF0	CONVERTER
G120X (690V,IP20,160kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YH50-1CP0	CONVERTER
G120X (690V,IP20,200kW,C3,USS,IOP-2,3C2)	6SL3220-3YH52-0CB0	CONVERTER
G120X (690V,IP20,200kW,C3,PN,IOP-2,3C2)	6SL3220-3YH52-0CF0	CONVERTER
G120X (690V,IP20,200kW,C3,DP,IOP-2,3C2)	6SL3220-3YH52-0CP0	CONVERTER
G120X (690V,IP20,200kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YH52-1CB0	CONVERTER
G120X (690V,IP20,200kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YH52-1CF0	CONVERTER
G120X (690V,IP20,200kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YH52-1CP0	CONVERTER
G120X (690V,IP20,250kW,C3,USS,IOP-2,3C2)	6SL3220-3YH54-0CB0	CONVERTER
G120X (690V,IP20,250kW,C3,PN,IOP-2,3C2)	6SL3220-3YH54-0CF0	CONVERTER
G120X (690V,IP20,250kW,C3,DP,IOP-2,3C2)	6SL3220-3YH54-0CP0	CONVERTER
G120X (690V,IP20,250kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YH54-1CB0	CONVERTER
G120X (690V,IP20,250kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YH54-1CF0	CONVERTER
G120X (690V,IP20,250kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YH54-1CP0	CONVERTER
G120X (690V,IP20,315kW,C3,USS,IOP-2,3C2)	6SL3220-3YH56-0CB0	CONVERTER
G120X (690V,IP20,315kW,C3,PN,IOP-2,3C2)	6SL3220-3YH56-0CF0	CONVERTER
G120X (690V,IP20,315kW,C3,DP,IOP-2,3C2)	6SL3220-3YH56-0CP0	CONVERTER
G120X (690V,IP20,315kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YH56-1CB0	CONVERTER
G120X (690V,IP20,315kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YH56-1CF0	CONVERTER
G120X (690V,IP20,315kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YH56-1CP0	CONVERTER
G120X (690V,IP20,355kW,C3,USS,IOP-2,3C2)	6SL3220-3YH58-0CB0	CONVERTER
G120X (690V,IP20,355kW,C3,PN,IOP-2,3C2)	6SL3220-3YH58-0CF0	CONVERTER

G120X (690V,IP20,355kW,C3,DP,IOP-2,3C2)	6SL3220-3YH58-0CP0	CONVERTER
G120X (690V,IP20,355kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YH58-1CB0	CONVERTER
G120X (690V,IP20,355kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YH58-1CF0	CONVERTER
G120X (690V,IP20,355kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YH58-1CP0	CONVERTER
G120X (690V,IP20,400kW,C3,USS,IOP-2,3C2)	6SL3220-3YH60-0CB0	CONVERTER
G120X (690V,IP20,400kW,C3,PN,IOP-2,3C2)	6SL3220-3YH60-0CF0	CONVERTER
G120X (690V,IP20,400kW,C3,DP,IOP-2,3C2)	6SL3220-3YH60-0CP0	CONVERTER
G120X (690V,IP20,400kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YH60-1CB0	CONVERTER
G120X (690V,IP20,400kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YH60-1CF0	CONVERTER
G120X (690V,IP20,400kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YH60-1CP0	CONVERTER
G120X (690V,IP20,450kW,C3,USS,IOP-2,3C2)	6SL3220-3YH62-0CB0	CONVERTER
G120X (690V,IP20,450kW,C3,PN,IOP-2,3C2)	6SL3220-3YH62-0CF0	CONVERTER
G120X (690V,IP20,450kW,C3,DP,IOP-2,3C2)	6SL3220-3YH62-0CP0	CONVERTER
G120X (690V,IP20,450kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YH62-1CB0	CONVERTER
G120X (690V,IP20,450kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YH62-1CF0	CONVERTER
G120X (690V,IP20,450kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YH62-1CP0	CONVERTER
G120X (690V,IP20,500kW,C3,USS,IOP-2,3C2)	6SL3220-3YH64-0CB0	CONVERTER
G120X (690V,IP20,500kW,C3,PN,IOP-2,3C2)	6SL3220-3YH64-0CF0	CONVERTER
G120X (690V,IP20,500kW,C3,DP,IOP-2,3C2)	6SL3220-3YH64-0CP0	CONVERTER
G120X (690V,IP20,500kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YH64-1CB0	CONVERTER
G120X (690V,IP20,500kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YH64-1CF0	CONVERTER
G120X (690V,IP20,500kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YH64-1CP0	CONVERTER
G120X (690V,IP20,560kW,C3,USS,IOP-2,3C2)	6SL3220-3YH66-0CB0	CONVERTER
G120X (690V,IP20,560kW,C3,PN,IOP-2,3C2)	6SL3220-3YH66-0CF0	CONVERTER
G120X (690V,IP20,560kW,C3,DP,IOP-2,3C2)	6SL3220-3YH66-0CP0	CONVERTER
G120X (690V,IP20,560kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YH66-1CB0	CONVERTER
G120X (690V,IP20,560kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YH66-1CF0	CONVERTER
G120X (690V,IP20,560kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YH66-1CP0	CONVERTER
G120X (690V,IP20,630kW,C3,USS,IOP-2,3C2)	6SL3220-3YH68-0CB0	CONVERTER
G120X (690V,IP20,630kW,C3,PN,IOP-2,3C2)	6SL3220-3YH68-0CF0	CONVERTER
G120X (690V,IP20,630kW,C3,DP,IOP-2,3C2)	6SL3220-3YH68-0CP0	CONVERTER
G120X (690V,IP20,630kW,C3,USS,IOP-2,3C2,IO)	6SL3220-3YH68-1CB0	CONVERTER
G120X (690V,IP20,630kW,C3,PN,IOP-2,3C2,IO)	6SL3220-3YH68-1CF0	CONVERTER
G120X (690V,IP20,630kW,C3,DP,IOP-2,3C2,IO)	6SL3220-3YH68-1CP0	CONVERTER
G120X (230V,IP20,0.75kW,UF,USS,Blanc,3C3)	6SL3230-1YC10-0UB0	CONVERTER
G120X (230V,IP20,0.75kW,UF,PN,Blanc,3C3)	6SL3230-1YC10-0UF0	CONVERTER
G120X (230V,IP20,0.75kW,UF,DP,Blanc,3C3)	6SL3230-1YC10-0UP0	CONVERTER
G120X (230V,IP20,0.75kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC10-1UB0	CONVERTER
G120X (230V,IP20,0.75kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC10-1UF0	CONVERTER
G120X (230V,IP20,0.75kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC10-1UP0	CONVERTER
G120X (230V,IP20,1.1kW,UF,USS,Blanc,3C3)	6SL3230-1YC12-0UB0	CONVERTER
G120X (230V,IP20,1.1kW,UF,PN,Blanc,3C3)	6SL3230-1YC12-0UF0	CONVERTER
G120X (230V,IP20,1.1kW,UF,DP,Blanc,3C3)	6SL3230-1YC12-0UP0	CONVERTER
G120X (230V,IP20,1.1kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC12-1UB0	CONVERTER

G120X (230V,IP20,1.1kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC12-1UF0	CONVERTER
G120X (230V,IP20,1.1kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC12-1UP0	CONVERTER
G120X (230V,IP20,1.5kW,UF,USS,Blanc,3C3)	6SL3230-1YC14-0UB0	CONVERTER
G120X (230V,IP20,1.5kW,UF,PN,Blanc,3C3)	6SL3230-1YC14-0UF0	CONVERTER
G120X (230V,IP20,1.5kW,UF,DP,Blanc,3C3)	6SL3230-1YC14-0UP0	CONVERTER
G120X (230V,IP20,1.5kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC14-1UB0	CONVERTER
G120X (230V,IP20,1.5kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC14-1UF0	CONVERTER
G120X (230V,IP20,1.5kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC14-1UP0	CONVERTER
G120X (230V,IP20,2.2kW,UF,USS,Blanc,3C3)	6SL3230-1YC16-0UB0	CONVERTER
G120X (230V,IP20,2.2kW,UF,PN,Blanc,3C3)	6SL3230-1YC16-0UF0	CONVERTER
G120X (230V,IP20,2.2kW,UF,DP,Blanc,3C3)	6SL3230-1YC16-0UP0	CONVERTER
G120X (230V,IP20,2.2kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC16-1UB0	CONVERTER
G120X (230V,IP20,2.2kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC16-1UF0	CONVERTER
G120X (230V,IP20,2.2kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC16-1UP0	CONVERTER
G120X (230V,IP20,3kW,UF,USS,Blanc,3C3)	6SL3230-1YC18-0UB0	CONVERTER
G120X (230V,IP20,3kW,UF,PN,Blanc,3C3)	6SL3230-1YC18-0UF0	CONVERTER
G120X (230V,IP20,3kW,UF,DP,Blanc,3C3)	6SL3230-1YC18-0UP0	CONVERTER
G120X (230V,IP20,3kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC18-1UB0	CONVERTER
G120X (230V,IP20,3kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC18-1UF0	CONVERTER
G120X (230V,IP20,3kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC18-1UP0	CONVERTER
G120X (230V,IP20,4kW,UF,USS,Blanc,3C3)	6SL3230-1YC20-0UB0	CONVERTER
G120X (230V,IP20,4kW,UF,PN,Blanc,3C3)	6SL3230-1YC20-0UF0	CONVERTER
G120X (230V,IP20,4kW,UF,DP,Blanc,3C3)	6SL3230-1YC20-0UP0	CONVERTER
G120X (230V,IP20,4kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC20-1UB0	CONVERTER
G120X (230V,IP20,4kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC20-1UF0	CONVERTER
G120X (230V,IP20,4kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC20-1UP0	CONVERTER
G120X (230V,IP20,5.5kW,UF,USS,Blanc,3C3)	6SL3230-1YC22-0UB0	CONVERTER
G120X (230V,IP20,5.5kW,UF,PN,Blanc,3C3)	6SL3230-1YC22-0UF0	CONVERTER
G120X (230V,IP20,5.5kW,UF,DP,Blanc,3C3)	6SL3230-1YC22-0UP0	CONVERTER
G120X (230V,IP20,5.5kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC22-1UB0	CONVERTER
G120X (230V,IP20,5.5kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC22-1UF0	CONVERTER
G120X (230V,IP20,5.5kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC22-1UP0	CONVERTER
G120X (230V,IP20,7.5kW,UF,USS,Blanc,3C3)	6SL3230-1YC24-0UB0	CONVERTER
G120X (230V,IP20,7.5kW,UF,PN,Blanc,3C3)	6SL3230-1YC24-0UF0	CONVERTER
G120X (230V,IP20,7.5kW,UF,DP,Blanc,3C3)	6SL3230-1YC24-0UP0	CONVERTER
G120X (230V,IP20,7.5kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC24-1UB0	CONVERTER
G120X (230V,IP20,7.5kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC24-1UF0	CONVERTER
G120X (230V,IP20,7.5kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC24-1UP0	CONVERTER
G120X (230V,IP20,11kW,UF,USS,Blanc,3C3)	6SL3230-1YC26-0UB0	CONVERTER
G120X (230V,IP20,11kW,UF,PN,Blanc,3C3)	6SL3230-1YC26-0UF0	CONVERTER
G120X (230V,IP20,11kW,UF,DP,Blanc,3C3)	6SL3230-1YC26-0UP0	CONVERTER
G120X (230V,IP20,11kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC26-1UB0	CONVERTER
G120X (230V,IP20,11kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC26-1UF0	CONVERTER
G120X (230V,IP20,11kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC26-1UP0	CONVERTER

G120X (230V,IP20,15kW,UF,USS,Blanc,3C3)	6SL3230-1YC28-0UB0	CONVERTER
G120X (230V,IP20,15kW,UF,PN,Blanc,3C3)	6SL3230-1YC28-0UF0	CONVERTER
G120X (230V,IP20,15kW,UF,DP,Blanc,3C3)	6SL3230-1YC28-0UP0	CONVERTER
G120X (230V,IP20,15kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC28-1UB0	CONVERTER
G120X (230V,IP20,15kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC28-1UF0	CONVERTER
G120X (230V,IP20,15kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC28-1UP0	CONVERTER
G120X (230V,IP20,18,5kW,UF,USS,Blanc,3C3)	6SL3230-1YC30-0UB0	CONVERTER
G120X (230V,IP20,18,5kW,UF,PN,Blanc,3C3)	6SL3230-1YC30-0UF0	CONVERTER
G120X (230V,IP20,18,5kW,UF,DP,Blanc,3C3)	6SL3230-1YC30-0UP0	CONVERTER
G120X (230V,IP20,18,5kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC30-1UB0	CONVERTER
G120X (230V,IP20,18,5kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC30-1UF0	CONVERTER
G120X (230V,IP20,18,5kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC30-1UP0	CONVERTER
G120X (230V,IP20,22kW,UF,USS,Blanc,3C3)	6SL3230-1YC32-0UB0	CONVERTER
G120X (230V,IP20,22kW,UF,PN,Blanc,3C3)	6SL3230-1YC32-0UF0	CONVERTER
G120X (230V,IP20,22kW,UF,DP,Blanc,3C3)	6SL3230-1YC32-0UP0	CONVERTER
G120X (230V,IP20,22kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC32-1UB0	CONVERTER
G120X (230V,IP20,22kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC32-1UF0	CONVERTER
G120X (230V,IP20,22kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC32-1UP0	CONVERTER
G120X (230V,IP20,30kW,UF,USS,Blanc,3C3)	6SL3230-1YC34-0UB0	CONVERTER
G120X (230V,IP20,30kW,UF,PN,Blanc,3C3)	6SL3230-1YC34-0UF0	CONVERTER
G120X (230V,IP20,30kW,UF,DP,Blanc,3C3)	6SL3230-1YC34-0UP0	CONVERTER
G120X (230V,IP20,30kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC34-1UB0	CONVERTER
G120X (230V,IP20,30kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC34-1UF0	CONVERTER
G120X (230V,IP20,30kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC34-1UP0	CONVERTER
G120X (230V,IP20,37kW,UF,USS,Blanc,3C3)	6SL3230-1YC36-0UB0	CONVERTER
G120X (230V,IP20,37kW,UF,PN,Blanc,3C3)	6SL3230-1YC36-0UF0	CONVERTER
G120X (230V,IP20,37kW,UF,DP,Blanc,3C3)	6SL3230-1YC36-0UP0	CONVERTER
G120X (230V,IP20,37kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC36-1UB0	CONVERTER
G120X (230V,IP20,37kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC36-1UF0	CONVERTER
G120X (230V,IP20,37kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC36-1UP0	CONVERTER
G120X (230V,IP20,45kW,UF,USS,Blanc,3C3)	6SL3230-1YC38-0UB0	CONVERTER
G120X (230V,IP20,45kW,UF,PN,Blanc,3C3)	6SL3230-1YC38-0UF0	CONVERTER
G120X (230V,IP20,45kW,UF,DP,Blanc,3C3)	6SL3230-1YC38-0UP0	CONVERTER
G120X (230V,IP20,45kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC38-1UB0	CONVERTER
G120X (230V,IP20,45kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC38-1UF0	CONVERTER
G120X (230V,IP20,45kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC38-1UP0	CONVERTER
G120X (230V,IP20,55kW,UF,USS,Blanc,3C3)	6SL3230-1YC40-0UB0	CONVERTER
G120X (230V,IP20,55kW,UF,PN,Blanc,3C3)	6SL3230-1YC40-0UF0	CONVERTER
G120X (230V,IP20,55kW,UF,DP,Blanc,3C3)	6SL3230-1YC40-0UP0	CONVERTER
G120X (230V,IP20,55kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YC40-1UB0	CONVERTER
G120X (230V,IP20,55kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YC40-1UF0	CONVERTER
G120X (230V,IP20,55kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YC40-1UP0	CONVERTER
G120X (400V,IP20,0.75kW,C2,USS,Blanc,3C3)	6SL3230-1YE10-0AB0	CONVERTER
G120X (400V,IP20,0.75kW,C2,PN,Blanc,3C3)	6SL3230-1YE10-0AF0	CONVERTER

G120X (400V,IP20,0.75kW,C2,DP,Blanc,3C3)	6SL3230-1YE10-0AP0	CONVERTER
G120X (400V,IP20,0.75kW,UF,USS,Blanc,3C3)	6SL3230-1YE10-0UB0	CONVERTER
G120X (400V,IP20,0.75kW,UF,PN,Blanc,3C3)	6SL3230-1YE10-0UF0	CONVERTER
G120X (400V,IP20,0.75kW,UF,DP,Blanc,3C3)	6SL3230-1YE10-0UP0	CONVERTER
G120X (400V,IP20,0.75kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE10-1AB0	CONVERTER
G120X (400V,IP20,0.75kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE10-1AF0	CONVERTER
G120X (400V,IP20,0.75kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE10-1AP0	CONVERTER
G120X (400V,IP20,0.75kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE10-1UB0	CONVERTER
G120X (400V,IP20,0.75kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE10-1UF0	CONVERTER
G120X (400V,IP20,0.75kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE10-1UP0	CONVERTER
G120X (400V,IP20,1.1kW,C2,USS,Blanc,3C3)	6SL3230-1YE12-0AB0	CONVERTER
G120X (400V,IP20,1.1kW,C2,PN,Blanc,3C3)	6SL3230-1YE12-0AF0	CONVERTER
G120X (400V,IP20,1.1kW,C2,DP,Blanc,3C3)	6SL3230-1YE12-0AP0	CONVERTER
G120X (400V,IP20,1.1kW,UF,USS,Blanc,3C3)	6SL3230-1YE12-0UB0	CONVERTER
G120X (400V,IP20,1.1kW,UF,PN,Blanc,3C3)	6SL3230-1YE12-0UF0	CONVERTER
G120X (400V,IP20,1.1kW,UF,DP,Blanc,3C3)	6SL3230-1YE12-0UP0	CONVERTER
G120X (400V,IP20,1.1kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE12-1AB0	CONVERTER
G120X (400V,IP20,1.1kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE12-1AF0	CONVERTER
G120X (400V,IP20,1.1kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE12-1AP0	CONVERTER
G120X (400V,IP20,1.1kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE12-1UB0	CONVERTER
G120X (400V,IP20,1.1kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE12-1UF0	CONVERTER
G120X (400V,IP20,1.1kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE12-1UP0	CONVERTER
G120X (400V,IP20,1.5kW,C2,USS,Blanc,3C3)	6SL3230-1YE14-0AB0	CONVERTER
G120X (400V,IP20,1.5kW,C2,PN,Blanc,3C3)	6SL3230-1YE14-0AF0	CONVERTER
G120X (400V,IP20,1.5kW,C2,DP,Blanc,3C3)	6SL3230-1YE14-0AP0	CONVERTER
G120X (400V,IP20,1.5kW,UF,USS,Blanc,3C3)	6SL3230-1YE14-0UB0	CONVERTER
G120X (400V,IP20,1.5kW,UF,PN,Blanc,3C3)	6SL3230-1YE14-0UF0	CONVERTER
G120X (400V,IP20,1.5kW,UF,DP,Blanc,3C3)	6SL3230-1YE14-0UP0	CONVERTER
G120X (400V,IP20,1.5kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE14-1AB0	CONVERTER
G120X (400V,IP20,1.5kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE14-1AF0	CONVERTER
G120X (400V,IP20,1.5kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE14-1AP0	CONVERTER
G120X (400V,IP20,1.5kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE14-1UB0	CONVERTER
G120X (400V,IP20,1.5kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE14-1UF0	CONVERTER
G120X (400V,IP20,1.5kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE14-1UP0	CONVERTER
G120X (400V,IP20,2.2kW,C2,USS,Blanc,3C3)	6SL3230-1YE16-0AB0	CONVERTER
G120X (400V,IP20,2.2kW,C2,PN,Blanc,3C3)	6SL3230-1YE16-0AF0	CONVERTER
G120X (400V,IP20,2.2kW,C2,DP,Blanc,3C3)	6SL3230-1YE16-0AP0	CONVERTER
G120X (400V,IP20,2.2kW,UF,USS,Blanc,3C3)	6SL3230-1YE16-0UB0	CONVERTER
G120X (400V,IP20,2.2kW,UF,PN,Blanc,3C3)	6SL3230-1YE16-0UF0	CONVERTER
G120X (400V,IP20,2.2kW,UF,DP,Blanc,3C3)	6SL3230-1YE16-0UP0	CONVERTER
G120X (400V,IP20,2.2kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE16-1AB0	CONVERTER
G120X (400V,IP20,2.2kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE16-1AF0	CONVERTER
G120X (400V,IP20,2.2kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE16-1AP0	CONVERTER
G120X (400V,IP20,2.2kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE16-1UB0	CONVERTER

G120X (400V,IP20,2.2kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE16-1UF0	CONVERTER
G120X (400V,IP20,2.2kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE16-1UP0	CONVERTER
G120X (400V,IP20,3kW,C2,USS,Blanc,3C3)	6SL3230-1YE18-0AB0	CONVERTER
G120X (400V,IP20,3kW,C2,PN,Blanc,3C3)	6SL3230-1YE18-0AF0	CONVERTER
G120X (400V,IP20,3kW,C2,DP,Blanc,3C3)	6SL3230-1YE18-0AP0	CONVERTER
G120X (400V,IP20,3kW,UF,USS,Blanc,3C3)	6SL3230-1YE18-0UB0	CONVERTER
G120X (400V,IP20,3kW,UF,PN,Blanc,3C3)	6SL3230-1YE18-0UF0	CONVERTER
G120X (400V,IP20,3kW,UF,DP,Blanc,3C3)	6SL3230-1YE18-0UP0	CONVERTER
G120X (400V,IP20,3kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE18-1AB0	CONVERTER
G120X (400V,IP20,3kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE18-1AF0	CONVERTER
G120X (400V,IP20,3kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE18-1AP0	CONVERTER
G120X (400V,IP20,3kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE18-1UB0	CONVERTER
G120X (400V,IP20,3kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE18-1UF0	CONVERTER
G120X (400V,IP20,3kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE18-1UP0	CONVERTER
G120X (400V,IP20,4kW,C2,USS,Blanc,3C3)	6SL3230-1YE20-0AB0	CONVERTER
G120X (400V,IP20,4kW,C2,PN,Blanc,3C3)	6SL3230-1YE20-0AF0	CONVERTER
G120X (400V,IP20,4kW,C2,DP,Blanc,3C3)	6SL3230-1YE20-0AP0	CONVERTER
G120X (400V,IP20,4kW,UF,USS,Blanc,3C3)	6SL3230-1YE20-0UB0	CONVERTER
G120X (400V,IP20,4kW,UF,PN,Blanc,3C3)	6SL3230-1YE20-0UF0	CONVERTER
G120X (400V,IP20,4kW,UF,DP,Blanc,3C3)	6SL3230-1YE20-0UP0	CONVERTER
G120X (400V,IP20,4kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE20-1AB0	CONVERTER
G120X (400V,IP20,4kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE20-1AF0	CONVERTER
G120X (400V,IP20,4kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE20-1AP0	CONVERTER
G120X (400V,IP20,4kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE20-1UB0	CONVERTER
G120X (400V,IP20,4kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE20-1UF0	CONVERTER
G120X (400V,IP20,4kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE20-1UP0	CONVERTER
G120X (400V,IP20,5.5kW,C2,USS,Blanc,3C3)	6SL3230-1YE22-0AB0	CONVERTER
G120X (400V,IP20,5.5kW,C2,PN,Blanc,3C3)	6SL3230-1YE22-0AF0	CONVERTER
G120X (400V,IP20,5.5kW,C2,DP,Blanc,3C3)	6SL3230-1YE22-0AP0	CONVERTER
G120X (400V,IP20,5.5kW,UF,USS,Blanc,3C3)	6SL3230-1YE22-0UB0	CONVERTER
G120X (400V,IP20,5.5kW,UF,PN,Blanc,3C3)	6SL3230-1YE22-0UF0	CONVERTER
G120X (400V,IP20,5.5kW,UF,DP,Blanc,3C3)	6SL3230-1YE22-0UP0	CONVERTER
G120X (400V,IP20,5.5kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE22-1AB0	CONVERTER
G120X (400V,IP20,5.5kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE22-1AF0	CONVERTER
G120X (400V,IP20,5.5kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE22-1AP0	CONVERTER
G120X (400V,IP20,5.5kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE22-1UB0	CONVERTER
G120X (400V,IP20,5.5kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE22-1UF0	CONVERTER
G120X (400V,IP20,5.5kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE22-1UP0	CONVERTER
G120X (400V,IP20,7.5kW,C2,USS,Blanc,3C3)	6SL3230-1YE24-0AB0	CONVERTER
G120X (400V,IP20,7.5kW,C2,PN,Blanc,3C3)	6SL3230-1YE24-0AF0	CONVERTER
G120X (400V,IP20,7.5kW,C2,DP,Blanc,3C3)	6SL3230-1YE24-0AP0	CONVERTER
G120X (400V,IP20,7.5kW,UF,USS,Blanc,3C3)	6SL3230-1YE24-0UB0	CONVERTER
G120X (400V,IP20,7.5kW,UF,PN,Blanc,3C3)	6SL3230-1YE24-0UF0	CONVERTER
G120X (400V,IP20,7.5kW,UF,DP,Blanc,3C3)	6SL3230-1YE24-0UP0	CONVERTER

G120X (400V,IP20,7.5kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE24-1AB0	CONVERTER
G120X (400V,IP20,7.5kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE24-1AF0	CONVERTER
G120X (400V,IP20,7.5kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE24-1AP0	CONVERTER
G120X (400V,IP20,7.5kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE24-1UB0	CONVERTER
G120X (400V,IP20,7.5kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE24-1UF0	CONVERTER
G120X (400V,IP20,7.5kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE24-1UP0	CONVERTER
G120X (400V,IP20,11kW,C2,USS,Blanc,3C3)	6SL3230-1YE26-0AB0	CONVERTER
G120X (400V,IP20,11kW,C2,PN,Blanc,3C3)	6SL3230-1YE26-0AF0	CONVERTER
G120X (400V,IP20,11kW,C2,DP,Blanc,3C3)	6SL3230-1YE26-0AP0	CONVERTER
G120X (400V,IP20,11kW,UF,USS,Blanc,3C3)	6SL3230-1YE26-0UB0	CONVERTER
G120X (400V,IP20,11kW,UF,PN,Blanc,3C3)	6SL3230-1YE26-0UF0	CONVERTER
G120X (400V,IP20,11kW,UF,DP,Blanc,3C3)	6SL3230-1YE26-0UP0	CONVERTER
G120X (400V,IP20,11kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE26-1AB0	CONVERTER
G120X (400V,IP20,11kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE26-1AF0	CONVERTER
G120X (400V,IP20,11kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE26-1AP0	CONVERTER
G120X (400V,IP20,11kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE26-1UB0	CONVERTER
G120X (400V,IP20,11kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE26-1UF0	CONVERTER
G120X (400V,IP20,11kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE26-1UP0	CONVERTER
G120X (400V,IP20,15kW,C2,USS,Blanc,3C3)	6SL3230-1YE28-0AB0	CONVERTER
G120X (400V,IP20,15kW,C2,PN,Blanc,3C3)	6SL3230-1YE28-0AF0	CONVERTER
G120X (400V,IP20,15kW,C2,DP,Blanc,3C3)	6SL3230-1YE28-0AP0	CONVERTER
G120X (400V,IP20,15kW,UF,USS,Blanc,3C3)	6SL3230-1YE28-0UB0	CONVERTER
G120X (400V,IP20,15kW,UF,PN,Blanc,3C3)	6SL3230-1YE28-0UF0	CONVERTER
G120X (400V,IP20,15kW,UF,DP,Blanc,3C3)	6SL3230-1YE28-0UP0	CONVERTER
G120X (400V,IP20,15kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE28-1AB0	CONVERTER
G120X (400V,IP20,15kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE28-1AF0	CONVERTER
G120X (400V,IP20,15kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE28-1AP0	CONVERTER
G120X (400V,IP20,15kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE28-1UB0	CONVERTER
G120X (400V,IP20,15kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE28-1UF0	CONVERTER
G120X (400V,IP20,15kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE28-1UP0	CONVERTER
G120X (400V,IP20,18,5kW,C2,USS,Blanc,3C3)	6SL3230-1YE30-0AB0	CONVERTER
G120X (400V,IP20,18,5kW,C2,PN,Blanc,3C3)	6SL3230-1YE30-0AF0	CONVERTER
G120X (400V,IP20,18,5kW,C2,DP,Blanc,3C3)	6SL3230-1YE30-0AP0	CONVERTER
G120X (400V,IP20,18,5kW,UF,USS,Blanc,3C3)	6SL3230-1YE30-0UB0	CONVERTER
G120X (400V,IP20,18,5kW,UF,PN,Blanc,3C3)	6SL3230-1YE30-0UF0	CONVERTER
G120X (400V,IP20,18,5kW,UF,DP,Blanc,3C3)	6SL3230-1YE30-0UP0	CONVERTER
G120X (400V,IP20,18,5kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE30-1AB0	CONVERTER
G120X (400V,IP20,18,5kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE30-1AF0	CONVERTER
G120X (400V,IP20,18,5kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE30-1AP0	CONVERTER
G120X (400V,IP20,18,5kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE30-1UB0	CONVERTER
G120X (400V,IP20,18,5kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE30-1UF0	CONVERTER
G120X (400V,IP20,18,5kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE30-1UP0	CONVERTER
G120X (400V,IP20,22kW,C2,USS,Blanc,3C3)	6SL3230-1YE32-0AB0	CONVERTER
G120X (400V,IP20,22kW,C2,PN,Blanc,3C3)	6SL3230-1YE32-0AF0	CONVERTER

G120X (400V,IP20,22kW,C2,DP,Blanc,3C3)	6SL3230-1YE32-0AP0	CONVERTER
G120X (400V,IP20,22kW,UF,USS,Blanc,3C3)	6SL3230-1YE32-0UB0	CONVERTER
G120X (400V,IP20,22kW,UF,PN,Blanc,3C3)	6SL3230-1YE32-0UF0	CONVERTER
G120X (400V,IP20,22kW,UF,DP,Blanc,3C3)	6SL3230-1YE32-0UP0	CONVERTER
G120X (400V,IP20,22kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE32-1AB0	CONVERTER
G120X (400V,IP20,22kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE32-1AF0	CONVERTER
G120X (400V,IP20,22kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE32-1AP0	CONVERTER
G120X (400V,IP20,22kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE32-1UB0	CONVERTER
G120X (400V,IP20,22kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE32-1UF0	CONVERTER
G120X (400V,IP20,22kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE32-1UP0	CONVERTER
G120X (400V,IP20,30kW,C2,USS,Blanc,3C3)	6SL3230-1YE34-0AB0	CONVERTER
G120X (400V,IP20,30kW,C2,PN,Blanc,3C3)	6SL3230-1YE34-0AF0	CONVERTER
G120X (400V,IP20,30kW,C2,DP,Blanc,3C3)	6SL3230-1YE34-0AP0	CONVERTER
G120X (400V,IP20,30kW,UF,USS,Blanc,3C3)	6SL3230-1YE34-0UB0	CONVERTER
G120X (400V,IP20,30kW,UF,PN,Blanc,3C3)	6SL3230-1YE34-0UF0	CONVERTER
G120X (400V,IP20,30kW,UF,DP,Blanc,3C3)	6SL3230-1YE34-0UP0	CONVERTER
G120X (400V,IP20,30kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE34-1AB0	CONVERTER
G120X (400V,IP20,30kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE34-1AF0	CONVERTER
G120X (400V,IP20,30kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE34-1AP0	CONVERTER
G120X (400V,IP20,30kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE34-1UB0	CONVERTER
G120X (400V,IP20,30kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE34-1UF0	CONVERTER
G120X (400V,IP20,30kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE34-1UP0	CONVERTER
G120X (400V,IP20,37kW,C2,USS,Blanc,3C3)	6SL3230-1YE36-0AB0	CONVERTER
G120X (400V,IP20,37kW,C2,PN,Blanc,3C3)	6SL3230-1YE36-0AF0	CONVERTER
G120X (400V,IP20,37kW,C2,DP,Blanc,3C3)	6SL3230-1YE36-0AP0	CONVERTER
G120X (400V,IP20,37kW,UF,USS,Blanc,3C3)	6SL3230-1YE36-0UB0	CONVERTER
G120X (400V,IP20,37kW,UF,PN,Blanc,3C3)	6SL3230-1YE36-0UF0	CONVERTER
G120X (400V,IP20,37kW,UF,DP,Blanc,3C3)	6SL3230-1YE36-0UP0	CONVERTER
G120X (400V,IP20,37kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE36-1AB0	CONVERTER
G120X (400V,IP20,37kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE36-1AF0	CONVERTER
G120X (400V,IP20,37kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE36-1AP0	CONVERTER
G120X (400V,IP20,37kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE36-1UB0	CONVERTER
G120X (400V,IP20,37kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE36-1UF0	CONVERTER
G120X (400V,IP20,37kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE36-1UP0	CONVERTER
G120X (400V,IP20,45kW,C2,USS,Blanc,3C3)	6SL3230-1YE38-0AB0	CONVERTER
G120X (400V,IP20,45kW,C2,PN,Blanc,3C3)	6SL3230-1YE38-0AF0	CONVERTER
G120X (400V,IP20,45kW,C2,DP,Blanc,3C3)	6SL3230-1YE38-0AP0	CONVERTER
G120X (400V,IP20,45kW,UF,USS,Blanc,3C3)	6SL3230-1YE38-0UB0	CONVERTER
G120X (400V,IP20,45kW,UF,PN,Blanc,3C3)	6SL3230-1YE38-0UF0	CONVERTER
G120X (400V,IP20,45kW,UF,DP,Blanc,3C3)	6SL3230-1YE38-0UP0	CONVERTER
G120X (400V,IP20,45kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE38-1AB0	CONVERTER
G120X (400V,IP20,45kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE38-1AF0	CONVERTER
G120X (400V,IP20,45kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE38-1AP0	CONVERTER
G120X (400V,IP20,45kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE38-1UB0	CONVERTER

G120X (400V,IP20,45kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE38-1UF0	CONVERTER
G120X (400V,IP20,45kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE38-1UP0	CONVERTER
G120X (400V,IP20,55kW,C2,USS,Blanc,3C3)	6SL3230-1YE40-0AB0	CONVERTER
G120X (400V,IP20,55kW,C2,PN,Blanc,3C3)	6SL3230-1YE40-0AF0	CONVERTER
G120X (400V,IP20,55kW,C2,DP,Blanc,3C3)	6SL3230-1YE40-0AP0	CONVERTER
G120X (400V,IP20,55kW,UF,USS,Blanc,3C3)	6SL3230-1YE40-0UB0	CONVERTER
G120X (400V,IP20,55kW,UF,PN,Blanc,3C3)	6SL3230-1YE40-0UF0	CONVERTER
G120X (400V,IP20,55kW,UF,DP,Blanc,3C3)	6SL3230-1YE40-0UP0	CONVERTER
G120X (400V,IP20,55kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE40-1AB0	CONVERTER
G120X (400V,IP20,55kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE40-1AF0	CONVERTER
G120X (400V,IP20,55kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE40-1AP0	CONVERTER
G120X (400V,IP20,55kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE40-1UB0	CONVERTER
G120X (400V,IP20,55kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE40-1UF0	CONVERTER
G120X (400V,IP20,55kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE40-1UP0	CONVERTER
G120X (400V,IP20,75kW,C2,USS,Blanc,3C3)	6SL3230-1YE42-0AB0	CONVERTER
G120X (400V,IP20,75kW,C2,PN,Blanc,3C3)	6SL3230-1YE42-0AF0	CONVERTER
G120X (400V,IP20,75kW,C2,DP,Blanc,3C3)	6SL3230-1YE42-0AP0	CONVERTER
G120X (400V,IP20,75kW,UF,USS,Blanc,3C3)	6SL3230-1YE42-0UB0	CONVERTER
G120X (400V,IP20,75kW,UF,PN,Blanc,3C3)	6SL3230-1YE42-0UF0	CONVERTER
G120X (400V,IP20,75kW,UF,DP,Blanc,3C3)	6SL3230-1YE42-0UP0	CONVERTER
G120X (400V,IP20,75kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE42-1AB0	CONVERTER
G120X (400V,IP20,75kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE42-1AF0	CONVERTER
G120X (400V,IP20,75kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE42-1AP0	CONVERTER
G120X (400V,IP20,75kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE42-1UB0	CONVERTER
G120X (400V,IP20,75kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE42-1UF0	CONVERTER
G120X (400V,IP20,75kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE42-1UP0	CONVERTER
G120X (400V,IP20,90kW,C2,USS,Blanc,3C3)	6SL3230-1YE44-0AB0	CONVERTER
G120X (400V,IP20,90kW,C2,PN,Blanc,3C3)	6SL3230-1YE44-0AF0	CONVERTER
G120X (400V,IP20,90kW,C2,DP,Blanc,3C3)	6SL3230-1YE44-0AP0	CONVERTER
G120X (400V,IP20,90kW,UF,USS,Blanc,3C3)	6SL3230-1YE44-0UB0	CONVERTER
G120X (400V,IP20,90kW,UF,PN,Blanc,3C3)	6SL3230-1YE44-0UF0	CONVERTER
G120X (400V,IP20,90kW,UF,DP,Blanc,3C3)	6SL3230-1YE44-0UP0	CONVERTER
G120X (400V,IP20,90kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE44-1AB0	CONVERTER
G120X (400V,IP20,90kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE44-1AF0	CONVERTER
G120X (400V,IP20,90kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE44-1AP0	CONVERTER
G120X (400V,IP20,90kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE44-1UB0	CONVERTER
G120X (400V,IP20,90kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE44-1UF0	CONVERTER
G120X (400V,IP20,90kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE44-1UP0	CONVERTER
G120X (400V,IP20,110kW,C2,USS,Blanc,3C3)	6SL3230-1YE46-0AB0	CONVERTER
G120X (400V,IP20,110kW,C2,PN,Blanc,3C3)	6SL3230-1YE46-0AF0	CONVERTER
G120X (400V,IP20,110kW,C2,DP,Blanc,3C3)	6SL3230-1YE46-0AP0	CONVERTER
G120X (400V,IP20,110kW,UF,USS,Blanc,3C3)	6SL3230-1YE46-0UB0	CONVERTER
G120X (400V,IP20,110kW,UF,PN,Blanc,3C3)	6SL3230-1YE46-0UF0	CONVERTER
G120X (400V,IP20,110kW,UF,DP,Blanc,3C3)	6SL3230-1YE46-0UP0	CONVERTER

G120X (400V,IP20,110kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE46-1AB0	CONVERTER
G120X (400V,IP20,110kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE46-1AF0	CONVERTER
G120X (400V,IP20,110kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE46-1AP0	CONVERTER
G120X (400V,IP20,110kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE46-1UB0	CONVERTER
G120X (400V,IP20,110kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE46-1UF0	CONVERTER
G120X (400V,IP20,110kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE46-1UP0	CONVERTER
G120X (400V,IP20,132kW,C2,USS,Blanc,3C3)	6SL3230-1YE48-0AB0	CONVERTER
G120X (400V,IP20,132kW,C2,PN,Blanc,3C3)	6SL3230-1YE48-0AF0	CONVERTER
G120X (400V,IP20,132kW,C2,DP,Blanc,3C3)	6SL3230-1YE48-0AP0	CONVERTER
G120X (400V,IP20,132kW,UF,USS,Blanc,3C3)	6SL3230-1YE48-0UB0	CONVERTER
G120X (400V,IP20,132kW,UF,PN,Blanc,3C3)	6SL3230-1YE48-0UF0	CONVERTER
G120X (400V,IP20,132kW,UF,DP,Blanc,3C3)	6SL3230-1YE48-0UP0	CONVERTER
G120X (400V,IP20,132kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE48-1AB0	CONVERTER
G120X (400V,IP20,132kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE48-1AF0	CONVERTER
G120X (400V,IP20,132kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE48-1AP0	CONVERTER
G120X (400V,IP20,132kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YE48-1UB0	CONVERTER
G120X (400V,IP20,132kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YE48-1UF0	CONVERTER
G120X (400V,IP20,132kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YE48-1UP0	CONVERTER
G120X (400V,IP20,160kW,C2,USS,Blanc,3C3)	6SL3230-1YE50-0AB0	CONVERTER
G120X (400V,IP20,160kW,C2,PN,Blanc,3C3)	6SL3230-1YE50-0AF0	CONVERTER
G120X (400V,IP20,160kW,C2,DP,Blanc,3C3)	6SL3230-1YE50-0AP0	CONVERTER
G120X (400V,IP20,160kW,C3,USS,Blanc,3C3)	6SL3230-1YE50-0CB0	CONVERTER
G120X (400V,IP20,160kW,C3,PN,Blanc,3C3)	6SL3230-1YE50-0CF0	CONVERTER
G120X (400V,IP20,160kW,C3,DP,Blanc,3C3)	6SL3230-1YE50-0CP0	CONVERTER
G120X (400V,IP20,160kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE50-1AB0	CONVERTER
G120X (400V,IP20,160kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE50-1AF0	CONVERTER
G120X (400V,IP20,160kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE50-1AP0	CONVERTER
G120X (400V,IP20,160kW,C3,USS,Blanc,3C3,IO)	6SL3230-1YE50-1CB0	CONVERTER
G120X (400V,IP20,160kW,C3,PN,Blanc,3C3,IO)	6SL3230-1YE50-1CF0	CONVERTER
G120X (400V,IP20,160kW,C3,DP,Blanc,3C3,IO)	6SL3230-1YE50-1CP0	CONVERTER
G120X (400V,IP20,200kW,C2,USS,Blanc,3C3)	6SL3230-1YE52-0AB0	CONVERTER
G120X (400V,IP20,200kW,C2,PN,Blanc,3C3)	6SL3230-1YE52-0AF0	CONVERTER
G120X (400V,IP20,200kW,C2,DP,Blanc,3C3)	6SL3230-1YE52-0AP0	CONVERTER
G120X (400V,IP20,200kW,C3,USS,Blanc,3C3)	6SL3230-1YE52-0CB0	CONVERTER
G120X (400V,IP20,200kW,C3,PN,Blanc,3C3)	6SL3230-1YE52-0CF0	CONVERTER
G120X (400V,IP20,200kW,C3,DP,Blanc,3C3)	6SL3230-1YE52-0CP0	CONVERTER
G120X (400V,IP20,200kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE52-1AB0	CONVERTER
G120X (400V,IP20,200kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE52-1AF0	CONVERTER
G120X (400V,IP20,200kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE52-1AP0	CONVERTER
G120X (400V,IP20,200kW,C3,USS,Blanc,3C3,IO)	6SL3230-1YE52-1CB0	CONVERTER
G120X (400V,IP20,200kW,C3,PN,Blanc,3C3,IO)	6SL3230-1YE52-1CF0	CONVERTER
G120X (400V,IP20,200kW,C3,DP,Blanc,3C3,IO)	6SL3230-1YE52-1CP0	CONVERTER
G120X (400V,IP20,250kW,C2,USS,Blanc,3C3)	6SL3230-1YE54-0AB0	CONVERTER
G120X (400V,IP20,250kW,C2,PN,Blanc,3C3)	6SL3230-1YE54-0AF0	CONVERTER

G120X (400V,IP20,250kW,C2,DP,Blanc,3C3)	6SL3230-1YE54-0AP0	CONVERTER
G120X (400V,IP20,250kW,C3,USS,Blanc,3C3)	6SL3230-1YE54-0CB0	CONVERTER
G120X (400V,IP20,250kW,C3,PN,Blanc,3C3)	6SL3230-1YE54-0CF0	CONVERTER
G120X (400V,IP20,250kW,C3,DP,Blanc,3C3)	6SL3230-1YE54-0CP0	CONVERTER
G120X (400V,IP20,250kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YE54-1AB0	CONVERTER
G120X (400V,IP20,250kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YE54-1AF0	CONVERTER
G120X (400V,IP20,250kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YE54-1AP0	CONVERTER
G120X (400V,IP20,250kW,C3,USS,Blanc,3C3,IO)	6SL3230-1YE54-1CB0	CONVERTER
G120X (400V,IP20,250kW,C3,PN,Blanc,3C3,IO)	6SL3230-1YE54-1CF0	CONVERTER
G120X (400V,IP20,250kW,C3,DP,Blanc,3C3,IO)	6SL3230-1YE54-1CP0	CONVERTER
G120X (690V,IP20,3kW,C2,USS,Blanc,3C3)	6SL3230-1YH18-0AB0	CONVERTER
G120X (690V,IP20,3kW,C2,PN,Blanc,3C3)	6SL3230-1YH18-0AF0	CONVERTER
G120X (690V,IP20,3kW,C2,DP,Blanc,3C3)	6SL3230-1YH18-0AP0	CONVERTER
G120X (690V,IP20,3kW,UF,USS,Blanc,3C3)	6SL3230-1YH18-0UB0	CONVERTER
G120X (690V,IP20,3kW,UF,PN,Blanc,3C3)	6SL3230-1YH18-0UF0	CONVERTER
G120X (690V,IP20,3kW,UF,DP,Blanc,3C3)	6SL3230-1YH18-0UP0	CONVERTER
G120X (690V,IP20,3kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YH18-1AB0	CONVERTER
G120X (690V,IP20,3kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YH18-1AF0	CONVERTER
G120X (690V,IP20,3kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YH18-1AP0	CONVERTER
G120X (690V,IP20,3kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH18-1UB0	CONVERTER
G120X (690V,IP20,3kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH18-1UF0	CONVERTER
G120X (690V,IP20,3kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH18-1UP0	CONVERTER
G120X (690V,IP20,4kW,C2,USS,Blanc,3C3)	6SL3230-1YH20-0AB0	CONVERTER
G120X (690V,IP20,4kW,C2,PN,Blanc,3C3)	6SL3230-1YH20-0AF0	CONVERTER
G120X (690V,IP20,4kW,C2,DP,Blanc,3C3)	6SL3230-1YH20-0AP0	CONVERTER
G120X (690V,IP20,4kW,UF,USS,Blanc,3C3)	6SL3230-1YH20-0UB0	CONVERTER
G120X (690V,IP20,4kW,UF,PN,Blanc,3C3)	6SL3230-1YH20-0UF0	CONVERTER
G120X (690V,IP20,4kW,UF,DP,Blanc,3C3)	6SL3230-1YH20-0UP0	CONVERTER
G120X (690V,IP20,4kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YH20-1AB0	CONVERTER
G120X (690V,IP20,4kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YH20-1AF0	CONVERTER
G120X (690V,IP20,4kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YH20-1AP0	CONVERTER
G120X (690V,IP20,4kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH20-1UB0	CONVERTER
G120X (690V,IP20,4kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH20-1UF0	CONVERTER
G120X (690V,IP20,4kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH20-1UP0	CONVERTER
G120X (690V,IP20,5.5kW,C2,USS,Blanc,3C3)	6SL3230-1YH22-0AB0	CONVERTER
G120X (690V,IP20,5.5kW,C2,PN,Blanc,3C3)	6SL3230-1YH22-0AF0	CONVERTER
G120X (690V,IP20,5.5kW,C2,DP,Blanc,3C3)	6SL3230-1YH22-0AP0	CONVERTER
G120X (690V,IP20,5.5kW,UF,USS,Blanc,3C3)	6SL3230-1YH22-0UB0	CONVERTER
G120X (690V,IP20,5.5kW,UF,PN,Blanc,3C3)	6SL3230-1YH22-0UF0	CONVERTER
G120X (690V,IP20,5.5kW,UF,DP,Blanc,3C3)	6SL3230-1YH22-0UP0	CONVERTER
G120X (690V,IP20,5.5kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YH22-1AB0	CONVERTER
G120X (690V,IP20,5.5kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YH22-1AF0	CONVERTER
G120X (690V,IP20,5.5kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YH22-1AP0	CONVERTER
G120X (690V,IP20,5.5kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH22-1UB0	CONVERTER

G120X (690V,IP20,5.5kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH22-1UF0	CONVERTER
G120X (690V,IP20,5.5kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH22-1UP0	CONVERTER
G120X (690V,IP20,7.5kW,C2,USS,Blanc,3C3)	6SL3230-1YH24-0AB0	CONVERTER
G120X (690V,IP20,7.5kW,C2,PN,Blanc,3C3)	6SL3230-1YH24-0AF0	CONVERTER
G120X (690V,IP20,7.5kW,C2,DP,Blanc,3C3)	6SL3230-1YH24-0AP0	CONVERTER
G120X (690V,IP20,7.5kW,UF,USS,Blanc,3C3)	6SL3230-1YH24-0UB0	CONVERTER
G120X (690V,IP20,7.5kW,UF,PN,Blanc,3C3)	6SL3230-1YH24-0UF0	CONVERTER
G120X (690V,IP20,7.5kW,UF,DP,Blanc,3C3)	6SL3230-1YH24-0UP0	CONVERTER
G120X (690V,IP20,7.5kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YH24-1AB0	CONVERTER
G120X (690V,IP20,7.5kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YH24-1AF0	CONVERTER
G120X (690V,IP20,7.5kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YH24-1AP0	CONVERTER
G120X (690V,IP20,7.5kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH24-1UB0	CONVERTER
G120X (690V,IP20,7.5kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH24-1UF0	CONVERTER
G120X (690V,IP20,7.5kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH24-1UP0	CONVERTER
G120X (690V,IP20,11kW,C2,USS,Blanc,3C3)	6SL3230-1YH26-0AB0	CONVERTER
G120X (690V,IP20,11kW,C2,PN,Blanc,3C3)	6SL3230-1YH26-0AF0	CONVERTER
G120X (690V,IP20,11kW,C2,DP,Blanc,3C3)	6SL3230-1YH26-0AP0	CONVERTER
G120X (690V,IP20,11kW,UF,USS,Blanc,3C3)	6SL3230-1YH26-0UB0	CONVERTER
G120X (690V,IP20,11kW,UF,PN,Blanc,3C3)	6SL3230-1YH26-0UF0	CONVERTER
G120X (690V,IP20,11kW,UF,DP,Blanc,3C3)	6SL3230-1YH26-0UP0	CONVERTER
G120X (690V,IP20,11kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YH26-1AB0	CONVERTER
G120X (690V,IP20,11kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YH26-1AF0	CONVERTER
G120X (690V,IP20,11kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YH26-1AP0	CONVERTER
G120X (690V,IP20,11kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH26-1UB0	CONVERTER
G120X (690V,IP20,11kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH26-1UF0	CONVERTER
G120X (690V,IP20,11kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH26-1UP0	CONVERTER
G120X (690V,IP20,15kW,C2,USS,Blanc,3C3)	6SL3230-1YH28-0AB0	CONVERTER
G120X (690V,IP20,15kW,C2,PN,Blanc,3C3)	6SL3230-1YH28-0AF0	CONVERTER
G120X (690V,IP20,15kW,C2,DP,Blanc,3C3)	6SL3230-1YH28-0AP0	CONVERTER
G120X (690V,IP20,15kW,UF,USS,Blanc,3C3)	6SL3230-1YH28-0UB0	CONVERTER
G120X (690V,IP20,15kW,UF,PN,Blanc,3C3)	6SL3230-1YH28-0UF0	CONVERTER
G120X (690V,IP20,15kW,UF,DP,Blanc,3C3)	6SL3230-1YH28-0UP0	CONVERTER
G120X (690V,IP20,15kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YH28-1AB0	CONVERTER
G120X (690V,IP20,15kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YH28-1AF0	CONVERTER
G120X (690V,IP20,15kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YH28-1AP0	CONVERTER
G120X (690V,IP20,15kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH28-1UB0	CONVERTER
G120X (690V,IP20,15kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH28-1UF0	CONVERTER
G120X (690V,IP20,15kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH28-1UP0	CONVERTER
G120X (690V,IP20,18,5kW,C2,USS,Blanc,3C3)	6SL3230-1YH30-0AB0	CONVERTER
G120X (690V,IP20,18,5kW,C2,PN,Blanc,3C3)	6SL3230-1YH30-0AF0	CONVERTER
G120X (690V,IP20,18,5kW,C2,DP,Blanc,3C3)	6SL3230-1YH30-0AP0	CONVERTER
G120X (690V,IP20,18,5kW,UF,USS,Blanc,3C3)	6SL3230-1YH30-0UB0	CONVERTER
G120X (690V,IP20,18,5kW,UF,PN,Blanc,3C3)	6SL3230-1YH30-0UF0	CONVERTER
G120X (690V,IP20,18,5kW,UF,DP,Blanc,3C3)	6SL3230-1YH30-0UP0	CONVERTER

G120X (690V,IP20,18,5kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YH30-1AB0	CONVERTER
G120X (690V,IP20,18,5kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YH30-1AF0	CONVERTER
G120X (690V,IP20,18,5kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YH30-1AP0	CONVERTER
G120X (690V,IP20,18,5kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH30-1UB0	CONVERTER
G120X (690V,IP20,18,5kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH30-1UF0	CONVERTER
G120X (690V,IP20,18,5kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH30-1UP0	CONVERTER
G120X (690V,IP20,22kW,C2,USS,Blanc,3C3)	6SL3230-1YH32-0AB0	CONVERTER
G120X (690V,IP20,22kW,C2,PN,Blanc,3C3)	6SL3230-1YH32-0AF0	CONVERTER
G120X (690V,IP20,22kW,C2,DP,Blanc,3C3)	6SL3230-1YH32-0AP0	CONVERTER
G120X (690V,IP20,22kW,UF,USS,Blanc,3C3)	6SL3230-1YH32-0UB0	CONVERTER
G120X (690V,IP20,22kW,UF,PN,Blanc,3C3)	6SL3230-1YH32-0UF0	CONVERTER
G120X (690V,IP20,22kW,UF,DP,Blanc,3C3)	6SL3230-1YH32-0UP0	CONVERTER
G120X (690V,IP20,22kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YH32-1AB0	CONVERTER
G120X (690V,IP20,22kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YH32-1AF0	CONVERTER
G120X (690V,IP20,22kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YH32-1AP0	CONVERTER
G120X (690V,IP20,22kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH32-1UB0	CONVERTER
G120X (690V,IP20,22kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH32-1UF0	CONVERTER
G120X (690V,IP20,22kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH32-1UP0	CONVERTER
G120X (690V,IP20,30kW,C2,USS,Blanc,3C3)	6SL3230-1YH34-0AB0	CONVERTER
G120X (690V,IP20,30kW,C2,PN,Blanc,3C3)	6SL3230-1YH34-0AF0	CONVERTER
G120X (690V,IP20,30kW,C2,DP,Blanc,3C3)	6SL3230-1YH34-0AP0	CONVERTER
G120X (690V,IP20,30kW,UF,USS,Blanc,3C3)	6SL3230-1YH34-0UB0	CONVERTER
G120X (690V,IP20,30kW,UF,PN,Blanc,3C3)	6SL3230-1YH34-0UF0	CONVERTER
G120X (690V,IP20,30kW,UF,DP,Blanc,3C3)	6SL3230-1YH34-0UP0	CONVERTER
G120X (690V,IP20,30kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YH34-1AB0	CONVERTER
G120X (690V,IP20,30kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YH34-1AF0	CONVERTER
G120X (690V,IP20,30kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YH34-1AP0	CONVERTER
G120X (690V,IP20,30kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH34-1UB0	CONVERTER
G120X (690V,IP20,30kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH34-1UF0	CONVERTER
G120X (690V,IP20,30kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH34-1UP0	CONVERTER
G120X (690V,IP20,37kW,C2,USS,Blanc,3C3)	6SL3230-1YH36-0AB0	CONVERTER
G120X (690V,IP20,37kW,C2,PN,Blanc,3C3)	6SL3230-1YH36-0AF0	CONVERTER
G120X (690V,IP20,37kW,C2,DP,Blanc,3C3)	6SL3230-1YH36-0AP0	CONVERTER
G120X (690V,IP20,37kW,UF,USS,Blanc,3C3)	6SL3230-1YH36-0UB0	CONVERTER
G120X (690V,IP20,37kW,UF,PN,Blanc,3C3)	6SL3230-1YH36-0UF0	CONVERTER
G120X (690V,IP20,37kW,UF,DP,Blanc,3C3)	6SL3230-1YH36-0UP0	CONVERTER
G120X (690V,IP20,37kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YH36-1AB0	CONVERTER
G120X (690V,IP20,37kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YH36-1AF0	CONVERTER
G120X (690V,IP20,37kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YH36-1AP0	CONVERTER
G120X (690V,IP20,37kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH36-1UB0	CONVERTER
G120X (690V,IP20,37kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH36-1UF0	CONVERTER
G120X (690V,IP20,37kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH36-1UP0	CONVERTER
G120X (690V,IP20,45kW,C2,USS,Blanc,3C3)	6SL3230-1YH38-0AB0	CONVERTER
G120X (690V,IP20,45kW,C2,PN,Blanc,3C3)	6SL3230-1YH38-0AF0	CONVERTER

G120X (690V,IP20,45kW,C2,DP,Blanc,3C3)	6SL3230-1YH38-0AP0	CONVERTER
G120X (690V,IP20,45kW,UF,USS,Blanc,3C3)	6SL3230-1YH38-0UB0	CONVERTER
G120X (690V,IP20,45kW,UF,PN,Blanc,3C3)	6SL3230-1YH38-0UF0	CONVERTER
G120X (690V,IP20,45kW,UF,DP,Blanc,3C3)	6SL3230-1YH38-0UP0	CONVERTER
G120X (690V,IP20,45kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YH38-1AB0	CONVERTER
G120X (690V,IP20,45kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YH38-1AF0	CONVERTER
G120X (690V,IP20,45kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YH38-1AP0	CONVERTER
G120X (690V,IP20,45kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH38-1UB0	CONVERTER
G120X (690V,IP20,45kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH38-1UF0	CONVERTER
G120X (690V,IP20,45kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH38-1UP0	CONVERTER
G120X (690V,IP20,55kW,C2,USS,Blanc,3C3)	6SL3230-1YH40-0AB0	CONVERTER
G120X (690V,IP20,55kW,C2,PN,Blanc,3C3)	6SL3230-1YH40-0AF0	CONVERTER
G120X (690V,IP20,55kW,C2,DP,Blanc,3C3)	6SL3230-1YH40-0AP0	CONVERTER
G120X (690V,IP20,55kW,UF,USS,Blanc,3C3)	6SL3230-1YH40-0UB0	CONVERTER
G120X (690V,IP20,55kW,UF,PN,Blanc,3C3)	6SL3230-1YH40-0UF0	CONVERTER
G120X (690V,IP20,55kW,UF,DP,Blanc,3C3)	6SL3230-1YH40-0UP0	CONVERTER
G120X (690V,IP20,55kW,C2,USS,Blanc,3C3,IO)	6SL3230-1YH40-1AB0	CONVERTER
G120X (690V,IP20,55kW,C2,PN,Blanc,3C3,IO)	6SL3230-1YH40-1AF0	CONVERTER
G120X (690V,IP20,55kW,C2,DP,Blanc,3C3,IO)	6SL3230-1YH40-1AP0	CONVERTER
G120X (690V,IP20,55kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH40-1UB0	CONVERTER
G120X (690V,IP20,55kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH40-1UF0	CONVERTER
G120X (690V,IP20,55kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH40-1UP0	CONVERTER
G120X (690V,IP20,75kW,C3,USS,Blanc,3C3)	6SL3230-1YH42-0CB0	CONVERTER
G120X (690V,IP20,75kW,C3,PN,Blanc,3C3)	6SL3230-1YH42-0CF0	CONVERTER
G120X (690V,IP20,75kW,C3,DP,Blanc,3C3)	6SL3230-1YH42-0CP0	CONVERTER
G120X (690V,IP20,75kW,UF,USS,Blanc,3C3)	6SL3230-1YH42-0UB0	CONVERTER
G120X (690V,IP20,75kW,UF,PN,Blanc,3C3)	6SL3230-1YH42-0UF0	CONVERTER
G120X (690V,IP20,75kW,UF,DP,Blanc,3C3)	6SL3230-1YH42-0UP0	CONVERTER
G120X (690V,IP20,75kW,C3,USS,Blanc,3C3,IO)	6SL3230-1YH42-1CB0	CONVERTER
G120X (690V,IP20,75kW,C3,PN,Blanc,3C3,IO)	6SL3230-1YH42-1CF0	CONVERTER
G120X (690V,IP20,75kW,C3,DP,Blanc,3C3,IO)	6SL3230-1YH42-1CP0	CONVERTER
G120X (690V,IP20,75kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH42-1UB0	CONVERTER
G120X (690V,IP20,75kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH42-1UF0	CONVERTER
G120X (690V,IP20,75kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH42-1UP0	CONVERTER
G120X (690V,IP20,90kW,C3,USS,Blanc,3C3)	6SL3230-1YH44-0CB0	CONVERTER
G120X (690V,IP20,90kW,C3,PN,Blanc,3C3)	6SL3230-1YH44-0CF0	CONVERTER
G120X (690V,IP20,90kW,C3,DP,Blanc,3C3)	6SL3230-1YH44-0CP0	CONVERTER
G120X (690V,IP20,90kW,UF,USS,Blanc,3C3)	6SL3230-1YH44-0UB0	CONVERTER
G120X (690V,IP20,90kW,UF,PN,Blanc,3C3)	6SL3230-1YH44-0UF0	CONVERTER
G120X (690V,IP20,90kW,UF,DP,Blanc,3C3)	6SL3230-1YH44-0UP0	CONVERTER
G120X (690V,IP20,90kW,C3,USS,Blanc,3C3,IO)	6SL3230-1YH44-1CB0	CONVERTER
G120X (690V,IP20,90kW,C3,PN,Blanc,3C3,IO)	6SL3230-1YH44-1CF0	CONVERTER
G120X (690V,IP20,90kW,C3,DP,Blanc,3C3,IO)	6SL3230-1YH44-1CP0	CONVERTER
G120X (690V,IP20,90kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH44-1UB0	CONVERTER

G120X (690V,IP20,90kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH44-1UF0	CONVERTER
G120X (690V,IP20,90kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH44-1UP0	CONVERTER
G120X (690V,IP20,110kW,C3,USS,Blanc,3C3)	6SL3230-1YH46-0CB0	CONVERTER
G120X (690V,IP20,110kW,C3,PN,Blanc,3C3)	6SL3230-1YH46-0CF0	CONVERTER
G120X (690V,IP20,110kW,C3,DP,Blanc,3C3)	6SL3230-1YH46-0CP0	CONVERTER
G120X (690V,IP20,110kW,UF,USS,Blanc,3C3)	6SL3230-1YH46-0UB0	CONVERTER
G120X (690V,IP20,110kW,UF,PN,Blanc,3C3)	6SL3230-1YH46-0UF0	CONVERTER
G120X (690V,IP20,110kW,UF,DP,Blanc,3C3)	6SL3230-1YH46-0UP0	CONVERTER
G120X (690V,IP20,110kW,C3,USS,Blanc,3C3,IO)	6SL3230-1YH46-1CB0	CONVERTER
G120X (690V,IP20,110kW,C3,PN,Blanc,3C3,IO)	6SL3230-1YH46-1CF0	CONVERTER
G120X (690V,IP20,110kW,C3,DP,Blanc,3C3,IO)	6SL3230-1YH46-1CP0	CONVERTER
G120X (690V,IP20,110kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH46-1UB0	CONVERTER
G120X (690V,IP20,110kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH46-1UF0	CONVERTER
G120X (690V,IP20,110kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH46-1UP0	CONVERTER
G120X (690V,IP20,132kW,C3,USS,Blanc,3C3)	6SL3230-1YH48-0CB0	CONVERTER
G120X (690V,IP20,132kW,C3,PN,Blanc,3C3)	6SL3230-1YH48-0CF0	CONVERTER
G120X (690V,IP20,132kW,C3,DP,Blanc,3C3)	6SL3230-1YH48-0CP0	CONVERTER
G120X (690V,IP20,132kW,UF,USS,Blanc,3C3)	6SL3230-1YH48-0UB0	CONVERTER
G120X (690V,IP20,132kW,UF,PN,Blanc,3C3)	6SL3230-1YH48-0UF0	CONVERTER
G120X (690V,IP20,132kW,UF,DP,Blanc,3C3)	6SL3230-1YH48-0UP0	CONVERTER
G120X (690V,IP20,132kW,C3,USS,Blanc,3C3,IO)	6SL3230-1YH48-1CB0	CONVERTER
G120X (690V,IP20,132kW,C3,PN,Blanc,3C3,IO)	6SL3230-1YH48-1CF0	CONVERTER
G120X (690V,IP20,132kW,C3,DP,Blanc,3C3,IO)	6SL3230-1YH48-1CP0	CONVERTER
G120X (690V,IP20,132kW,UF,USS,Blanc,3C3,IO)	6SL3230-1YH48-1UB0	CONVERTER
G120X (690V,IP20,132kW,UF,PN,Blanc,3C3,IO)	6SL3230-1YH48-1UF0	CONVERTER
G120X (690V,IP20,132kW,UF,DP,Blanc,3C3,IO)	6SL3230-1YH48-1UP0	CONVERTER
G120X (690V,IP20,160kW,C3,USS,Blanc,3C3)	6SL3230-1YH50-0CB0	CONVERTER
G120X (690V,IP20,160kW,C3,PN,Blanc,3C3)	6SL3230-1YH50-0CF0	CONVERTER
G120X (690V,IP20,160kW,C3,DP,Blanc,3C3)	6SL3230-1YH50-0CP0	CONVERTER
G120X (690V,IP20,160kW,C3,USS,Blanc,3C3,IO)	6SL3230-1YH50-1CB0	CONVERTER
G120X (690V,IP20,160kW,C3,PN,Blanc,3C3,IO)	6SL3230-1YH50-1CF0	CONVERTER
G120X (690V,IP20,160kW,C3,DP,Blanc,3C3,IO)	6SL3230-1YH50-1CP0	CONVERTER
G120X (690V,IP20,200kW,C3,USS,Blanc,3C3)	6SL3230-1YH52-0CB0	CONVERTER
G120X (690V,IP20,200kW,C3,PN,Blanc,3C3)	6SL3230-1YH52-0CF0	CONVERTER
G120X (690V,IP20,200kW,C3,DP,Blanc,3C3)	6SL3230-1YH52-0CP0	CONVERTER
G120X (690V,IP20,200kW,C3,USS,Blanc,3C3,IO)	6SL3230-1YH52-1CB0	CONVERTER
G120X (690V,IP20,200kW,C3,PN,Blanc,3C3,IO)	6SL3230-1YH52-1CF0	CONVERTER
G120X (690V,IP20,200kW,C3,DP,Blanc,3C3,IO)	6SL3230-1YH52-1CP0	CONVERTER
G120X (690V,IP20,250kW,C3,USS,Blanc,3C3)	6SL3230-1YH54-0CB0	CONVERTER
G120X (690V,IP20,250kW,C3,PN,Blanc,3C3)	6SL3230-1YH54-0CF0	CONVERTER
G120X (690V,IP20,250kW,C3,DP,Blanc,3C3)	6SL3230-1YH54-0CP0	CONVERTER
G120X (690V,IP20,250kW,C3,USS,Blanc,3C3,IO)	6SL3230-1YH54-1CB0	CONVERTER
G120X (690V,IP20,250kW,C3,PN,Blanc,3C3,IO)	6SL3230-1YH54-1CF0	CONVERTER
G120X (690V,IP20,250kW,C3,DP,Blanc,3C3,IO)	6SL3230-1YH54-1CP0	CONVERTER

G120X (230V,IP20,0.75kW,UF,USS,BOP-2,3C3)	6SL3230-2YC10-0UB0	CONVERTER
G120X (230V,IP20,0.75kW,UF,PN,BOP-2,3C3)	6SL3230-2YC10-0UF0	CONVERTER
G120X (230V,IP20,0.75kW,UF,DP,BOP-2,3C3)	6SL3230-2YC10-0UP0	CONVERTER
G120X (230V,IP20,0.75kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC10-1UB0	CONVERTER
G120X (230V,IP20,0.75kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC10-1UF0	CONVERTER
G120X (230V,IP20,0.75kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC10-1UP0	CONVERTER
G120X (230V,IP20,1.1kW,UF,USS,BOP-2,3C3)	6SL3230-2YC12-0UB0	CONVERTER
G120X (230V,IP20,1.1kW,UF,PN,BOP-2,3C3)	6SL3230-2YC12-0UF0	CONVERTER
G120X (230V,IP20,1.1kW,UF,DP,BOP-2,3C3)	6SL3230-2YC12-0UP0	CONVERTER
G120X (230V,IP20,1.1kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC12-1UB0	CONVERTER
G120X (230V,IP20,1.1kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC12-1UF0	CONVERTER
G120X (230V,IP20,1.1kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC12-1UP0	CONVERTER
G120X (230V,IP20,1.5kW,UF,USS,BOP-2,3C3)	6SL3230-2YC14-0UB0	CONVERTER
G120X (230V,IP20,1.5kW,UF,PN,BOP-2,3C3)	6SL3230-2YC14-0UF0	CONVERTER
G120X (230V,IP20,1.5kW,UF,DP,BOP-2,3C3)	6SL3230-2YC14-0UP0	CONVERTER
G120X (230V,IP20,1.5kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC14-1UB0	CONVERTER
G120X (230V,IP20,1.5kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC14-1UF0	CONVERTER
G120X (230V,IP20,1.5kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC14-1UP0	CONVERTER
G120X (230V,IP20,2.2kW,UF,USS,BOP-2,3C3)	6SL3230-2YC16-0UB0	CONVERTER
G120X (230V,IP20,2.2kW,UF,PN,BOP-2,3C3)	6SL3230-2YC16-0UF0	CONVERTER
G120X (230V,IP20,2.2kW,UF,DP,BOP-2,3C3)	6SL3230-2YC16-0UP0	CONVERTER
G120X (230V,IP20,2.2kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC16-1UB0	CONVERTER
G120X (230V,IP20,2.2kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC16-1UF0	CONVERTER
G120X (230V,IP20,2.2kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC16-1UP0	CONVERTER
G120X (230V,IP20,3kW,UF,USS,BOP-2,3C3)	6SL3230-2YC18-0UB0	CONVERTER
G120X (230V,IP20,3kW,UF,PN,BOP-2,3C3)	6SL3230-2YC18-0UF0	CONVERTER
G120X (230V,IP20,3kW,UF,DP,BOP-2,3C3)	6SL3230-2YC18-0UP0	CONVERTER
G120X (230V,IP20,3kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC18-1UB0	CONVERTER
G120X (230V,IP20,3kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC18-1UF0	CONVERTER
G120X (230V,IP20,3kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC18-1UP0	CONVERTER
G120X (230V,IP20,4kW,UF,USS,BOP-2,3C3)	6SL3230-2YC20-0UB0	CONVERTER
G120X (230V,IP20,4kW,UF,PN,BOP-2,3C3)	6SL3230-2YC20-0UF0	CONVERTER
G120X (230V,IP20,4kW,UF,DP,BOP-2,3C3)	6SL3230-2YC20-0UP0	CONVERTER
G120X (230V,IP20,4kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC20-1UB0	CONVERTER
G120X (230V,IP20,4kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC20-1UF0	CONVERTER
G120X (230V,IP20,4kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC20-1UP0	CONVERTER
G120X (230V,IP20,5.5kW,UF,USS,BOP-2,3C3)	6SL3230-2YC22-0UB0	CONVERTER
G120X (230V,IP20,5.5kW,UF,PN,BOP-2,3C3)	6SL3230-2YC22-0UF0	CONVERTER
G120X (230V,IP20,5.5kW,UF,DP,BOP-2,3C3)	6SL3230-2YC22-0UP0	CONVERTER
G120X (230V,IP20,5.5kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC22-1UB0	CONVERTER
G120X (230V,IP20,5.5kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC22-1UF0	CONVERTER
G120X (230V,IP20,5.5kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC22-1UP0	CONVERTER
G120X (230V,IP20,7.5kW,UF,USS,BOP-2,3C3)	6SL3230-2YC24-0UB0	CONVERTER
G120X (230V,IP20,7.5kW,UF,PN,BOP-2,3C3)	6SL3230-2YC24-0UF0	CONVERTER

G120X (230V,IP20,7.5kW,UF,DP,BOP-2,3C3)	6SL3230-2YC24-0UP0	CONVERTER
G120X (230V,IP20,7.5kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC24-1UB0	CONVERTER
G120X (230V,IP20,7.5kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC24-1UF0	CONVERTER
G120X (230V,IP20,7.5kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC24-1UP0	CONVERTER
G120X (230V,IP20,11kW,UF,USS,BOP-2,3C3)	6SL3230-2YC26-0UB0	CONVERTER
G120X (230V,IP20,11kW,UF,PN,BOP-2,3C3)	6SL3230-2YC26-0UF0	CONVERTER
G120X (230V,IP20,11kW,UF,DP,BOP-2,3C3)	6SL3230-2YC26-0UP0	CONVERTER
G120X (230V,IP20,11kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC26-1UB0	CONVERTER
G120X (230V,IP20,11kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC26-1UF0	CONVERTER
G120X (230V,IP20,11kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC26-1UP0	CONVERTER
G120X (230V,IP20,15kW,UF,USS,BOP-2,3C3)	6SL3230-2YC28-0UB0	CONVERTER
G120X (230V,IP20,15kW,UF,PN,BOP-2,3C3)	6SL3230-2YC28-0UF0	CONVERTER
G120X (230V,IP20,15kW,UF,DP,BOP-2,3C3)	6SL3230-2YC28-0UP0	CONVERTER
G120X (230V,IP20,15kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC28-1UB0	CONVERTER
G120X (230V,IP20,15kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC28-1UF0	CONVERTER
G120X (230V,IP20,15kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC28-1UP0	CONVERTER
G120X (230V,IP20,18,5kW,UF,USS,BOP-2,3C3)	6SL3230-2YC30-0UB0	CONVERTER
G120X (230V,IP20,18,5kW,UF,PN,BOP-2,3C3)	6SL3230-2YC30-0UF0	CONVERTER
G120X (230V,IP20,18,5kW,UF,DP,BOP-2,3C3)	6SL3230-2YC30-0UP0	CONVERTER
G120X (230V,IP20,18,5kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC30-1UB0	CONVERTER
G120X (230V,IP20,18,5kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC30-1UF0	CONVERTER
G120X (230V,IP20,18,5kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC30-1UP0	CONVERTER
G120X (230V,IP20,22kW,UF,USS,BOP-2,3C3)	6SL3230-2YC32-0UB0	CONVERTER
G120X (230V,IP20,22kW,UF,PN,BOP-2,3C3)	6SL3230-2YC32-0UF0	CONVERTER
G120X (230V,IP20,22kW,UF,DP,BOP-2,3C3)	6SL3230-2YC32-0UP0	CONVERTER
G120X (230V,IP20,22kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC32-1UB0	CONVERTER
G120X (230V,IP20,22kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC32-1UF0	CONVERTER
G120X (230V,IP20,22kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC32-1UP0	CONVERTER
G120X (230V,IP20,30kW,UF,USS,BOP-2,3C3)	6SL3230-2YC34-0UB0	CONVERTER
G120X (230V,IP20,30kW,UF,PN,BOP-2,3C3)	6SL3230-2YC34-0UF0	CONVERTER
G120X (230V,IP20,30kW,UF,DP,BOP-2,3C3)	6SL3230-2YC34-0UP0	CONVERTER
G120X (230V,IP20,30kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC34-1UB0	CONVERTER
G120X (230V,IP20,30kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC34-1UF0	CONVERTER
G120X (230V,IP20,30kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC34-1UP0	CONVERTER
G120X (230V,IP20,37kW,UF,USS,BOP-2,3C3)	6SL3230-2YC36-0UB0	CONVERTER
G120X (230V,IP20,37kW,UF,PN,BOP-2,3C3)	6SL3230-2YC36-0UF0	CONVERTER
G120X (230V,IP20,37kW,UF,DP,BOP-2,3C3)	6SL3230-2YC36-0UP0	CONVERTER
G120X (230V,IP20,37kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC36-1UB0	CONVERTER
G120X (230V,IP20,37kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC36-1UF0	CONVERTER
G120X (230V,IP20,37kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC36-1UP0	CONVERTER
G120X (230V,IP20,45kW,UF,USS,BOP-2,3C3)	6SL3230-2YC38-0UB0	CONVERTER
G120X (230V,IP20,45kW,UF,PN,BOP-2,3C3)	6SL3230-2YC38-0UF0	CONVERTER
G120X (230V,IP20,45kW,UF,DP,BOP-2,3C3)	6SL3230-2YC38-0UP0	CONVERTER
G120X (230V,IP20,45kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC38-1UB0	CONVERTER

G120X (230V,IP20,45kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC38-1UF0	CONVERTER
G120X (230V,IP20,45kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC38-1UP0	CONVERTER
G120X (230V,IP20,55kW,UF,USS,BOP-2,3C3)	6SL3230-2YC40-0UB0	CONVERTER
G120X (230V,IP20,55kW,UF,PN,BOP-2,3C3)	6SL3230-2YC40-0UF0	CONVERTER
G120X (230V,IP20,55kW,UF,DP,BOP-2,3C3)	6SL3230-2YC40-0UP0	CONVERTER
G120X (230V,IP20,55kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YC40-1UB0	CONVERTER
G120X (230V,IP20,55kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YC40-1UF0	CONVERTER
G120X (230V,IP20,55kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YC40-1UP0	CONVERTER
G120X (400V,IP20,0.75kW,C2,USS,BOP-2,3C3)	6SL3230-2YE10-0AB0	CONVERTER
G120X (400V,IP20,0.75kW,C2,PN,BOP-2,3C3)	6SL3230-2YE10-0AF0	CONVERTER
G120X (400V,IP20,0.75kW,C2,DP,BOP-2,3C3)	6SL3230-2YE10-0AP0	CONVERTER
G120X (400V,IP20,0.75kW,UF,USS,BOP-2,3C3)	6SL3230-2YE10-0UB0	CONVERTER
G120X (400V,IP20,0.75kW,UF,PN,BOP-2,3C3)	6SL3230-2YE10-0UF0	CONVERTER
G120X (400V,IP20,0.75kW,UF,DP,BOP-2,3C3)	6SL3230-2YE10-0UP0	CONVERTER
G120X (400V,IP20,0.75kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE10-1AB0	CONVERTER
G120X (400V,IP20,0.75kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE10-1AF0	CONVERTER
G120X (400V,IP20,0.75kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE10-1AP0	CONVERTER
G120X (400V,IP20,0.75kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE10-1UB0	CONVERTER
G120X (400V,IP20,0.75kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE10-1UF0	CONVERTER
G120X (400V,IP20,0.75kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE10-1UP0	CONVERTER
G120X (400V,IP20,1.1kW,C2,USS,BOP-2,3C3)	6SL3230-2YE12-0AB0	CONVERTER
G120X (400V,IP20,1.1kW,C2,PN,BOP-2,3C3)	6SL3230-2YE12-0AF0	CONVERTER
G120X (400V,IP20,1.1kW,C2,DP,BOP-2,3C3)	6SL3230-2YE12-0AP0	CONVERTER
G120X (400V,IP20,1.1kW,UF,USS,BOP-2,3C3)	6SL3230-2YE12-0UB0	CONVERTER
G120X (400V,IP20,1.1kW,UF,PN,BOP-2,3C3)	6SL3230-2YE12-0UF0	CONVERTER
G120X (400V,IP20,1.1kW,UF,DP,BOP-2,3C3)	6SL3230-2YE12-0UP0	CONVERTER
G120X (400V,IP20,1.1kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE12-1AB0	CONVERTER
G120X (400V,IP20,1.1kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE12-1AF0	CONVERTER
G120X (400V,IP20,1.1kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE12-1AP0	CONVERTER
G120X (400V,IP20,1.1kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE12-1UB0	CONVERTER
G120X (400V,IP20,1.1kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE12-1UF0	CONVERTER
G120X (400V,IP20,1.1kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE12-1UP0	CONVERTER
G120X (400V,IP20,1.5kW,C2,USS,BOP-2,3C3)	6SL3230-2YE14-0AB0	CONVERTER
G120X (400V,IP20,1.5kW,C2,PN,BOP-2,3C3)	6SL3230-2YE14-0AF0	CONVERTER
G120X (400V,IP20,1.5kW,C2,DP,BOP-2,3C3)	6SL3230-2YE14-0AP0	CONVERTER
G120X (400V,IP20,1.5kW,UF,USS,BOP-2,3C3)	6SL3230-2YE14-0UB0	CONVERTER
G120X (400V,IP20,1.5kW,UF,PN,BOP-2,3C3)	6SL3230-2YE14-0UF0	CONVERTER
G120X (400V,IP20,1.5kW,UF,DP,BOP-2,3C3)	6SL3230-2YE14-0UP0	CONVERTER
G120X (400V,IP20,1.5kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE14-1AB0	CONVERTER
G120X (400V,IP20,1.5kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE14-1AF0	CONVERTER
G120X (400V,IP20,1.5kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE14-1AP0	CONVERTER
G120X (400V,IP20,1.5kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE14-1UB0	CONVERTER
G120X (400V,IP20,1.5kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE14-1UF0	CONVERTER
G120X (400V,IP20,1.5kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE14-1UP0	CONVERTER

G120X (400V,IP20,2.2kW,C2,USS,BOP-2,3C3)	6SL3230-2YE16-0AB0	CONVERTER
G120X (400V,IP20,2.2kW,C2,PN,BOP-2,3C3)	6SL3230-2YE16-0AF0	CONVERTER
G120X (400V,IP20,2.2kW,C2,DP,BOP-2,3C3)	6SL3230-2YE16-0AP0	CONVERTER
G120X (400V,IP20,2.2kW,UF,USS,BOP-2,3C3)	6SL3230-2YE16-0UB0	CONVERTER
G120X (400V,IP20,2.2kW,UF,PN,BOP-2,3C3)	6SL3230-2YE16-0UF0	CONVERTER
G120X (400V,IP20,2.2kW,UF,DP,BOP-2,3C3)	6SL3230-2YE16-0UP0	CONVERTER
G120X (400V,IP20,2.2kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE16-1AB0	CONVERTER
G120X (400V,IP20,2.2kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE16-1AF0	CONVERTER
G120X (400V,IP20,2.2kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE16-1AP0	CONVERTER
G120X (400V,IP20,2.2kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE16-1UB0	CONVERTER
G120X (400V,IP20,2.2kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE16-1UF0	CONVERTER
G120X (400V,IP20,2.2kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE16-1UP0	CONVERTER
G120X (400V,IP20,3kW,C2,USS,BOP-2,3C3)	6SL3230-2YE18-0AB0	CONVERTER
G120X (400V,IP20,3kW,C2,PN,BOP-2,3C3)	6SL3230-2YE18-0AF0	CONVERTER
G120X (400V,IP20,3kW,C2,DP,BOP-2,3C3)	6SL3230-2YE18-0AP0	CONVERTER
G120X (400V,IP20,3kW,UF,USS,BOP-2,3C3)	6SL3230-2YE18-0UB0	CONVERTER
G120X (400V,IP20,3kW,UF,PN,BOP-2,3C3)	6SL3230-2YE18-0UF0	CONVERTER
G120X (400V,IP20,3kW,UF,DP,BOP-2,3C3)	6SL3230-2YE18-0UP0	CONVERTER
G120X (400V,IP20,3kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE18-1AB0	CONVERTER
G120X (400V,IP20,3kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE18-1AF0	CONVERTER
G120X (400V,IP20,3kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE18-1AP0	CONVERTER
G120X (400V,IP20,3kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE18-1UB0	CONVERTER
G120X (400V,IP20,3kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE18-1UF0	CONVERTER
G120X (400V,IP20,3kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE18-1UP0	CONVERTER
G120X (400V,IP20,4kW,C2,USS,BOP-2,3C3)	6SL3230-2YE20-0AB0	CONVERTER
G120X (400V,IP20,4kW,C2,PN,BOP-2,3C3)	6SL3230-2YE20-0AF0	CONVERTER
G120X (400V,IP20,4kW,C2,DP,BOP-2,3C3)	6SL3230-2YE20-0AP0	CONVERTER
G120X (400V,IP20,4kW,UF,USS,BOP-2,3C3)	6SL3230-2YE20-0UB0	CONVERTER
G120X (400V,IP20,4kW,UF,PN,BOP-2,3C3)	6SL3230-2YE20-0UF0	CONVERTER
G120X (400V,IP20,4kW,UF,DP,BOP-2,3C3)	6SL3230-2YE20-0UP0	CONVERTER
G120X (400V,IP20,4kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE20-1AB0	CONVERTER
G120X (400V,IP20,4kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE20-1AF0	CONVERTER
G120X (400V,IP20,4kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE20-1AP0	CONVERTER
G120X (400V,IP20,4kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE20-1UB0	CONVERTER
G120X (400V,IP20,4kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE20-1UF0	CONVERTER
G120X (400V,IP20,4kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE20-1UP0	CONVERTER
G120X (400V,IP20,5.5kW,C2,USS,BOP-2,3C3)	6SL3230-2YE22-0AB0	CONVERTER
G120X (400V,IP20,5.5kW,C2,PN,BOP-2,3C3)	6SL3230-2YE22-0AF0	CONVERTER
G120X (400V,IP20,5.5kW,C2,DP,BOP-2,3C3)	6SL3230-2YE22-0AP0	CONVERTER
G120X (400V,IP20,5.5kW,UF,USS,BOP-2,3C3)	6SL3230-2YE22-0UB0	CONVERTER
G120X (400V,IP20,5.5kW,UF,PN,BOP-2,3C3)	6SL3230-2YE22-0UF0	CONVERTER
G120X (400V,IP20,5.5kW,UF,DP,BOP-2,3C3)	6SL3230-2YE22-0UP0	CONVERTER
G120X (400V,IP20,5.5kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE22-1AB0	CONVERTER
G120X (400V,IP20,5.5kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE22-1AF0	CONVERTER

G120X (400V,IP20,5.5kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE22-1AP0	CONVERTER
G120X (400V,IP20,5.5kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE22-1UB0	CONVERTER
G120X (400V,IP20,5.5kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE22-1UF0	CONVERTER
G120X (400V,IP20,5.5kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE22-1UP0	CONVERTER
G120X (400V,IP20,7.5kW,C2,USS,BOP-2,3C3)	6SL3230-2YE24-0AB0	CONVERTER
G120X (400V,IP20,7.5kW,C2,PN,BOP-2,3C3)	6SL3230-2YE24-0AF0	CONVERTER
G120X (400V,IP20,7.5kW,C2,DP,BOP-2,3C3)	6SL3230-2YE24-0AP0	CONVERTER
G120X (400V,IP20,7.5kW,UF,USS,BOP-2,3C3)	6SL3230-2YE24-0UB0	CONVERTER
G120X (400V,IP20,7.5kW,UF,PN,BOP-2,3C3)	6SL3230-2YE24-0UF0	CONVERTER
G120X (400V,IP20,7.5kW,UF,DP,BOP-2,3C3)	6SL3230-2YE24-0UP0	CONVERTER
G120X (400V,IP20,7.5kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE24-1AB0	CONVERTER
G120X (400V,IP20,7.5kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE24-1AF0	CONVERTER
G120X (400V,IP20,7.5kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE24-1AP0	CONVERTER
G120X (400V,IP20,7.5kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE24-1UB0	CONVERTER
G120X (400V,IP20,7.5kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE24-1UF0	CONVERTER
G120X (400V,IP20,7.5kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE24-1UP0	CONVERTER
G120X (400V,IP20,11kW,C2,USS,BOP-2,3C3)	6SL3230-2YE26-0AB0	CONVERTER
G120X (400V,IP20,11kW,C2,PN,BOP-2,3C3)	6SL3230-2YE26-0AF0	CONVERTER
G120X (400V,IP20,11kW,C2,DP,BOP-2,3C3)	6SL3230-2YE26-0AP0	CONVERTER
G120X (400V,IP20,11kW,UF,USS,BOP-2,3C3)	6SL3230-2YE26-0UB0	CONVERTER
G120X (400V,IP20,11kW,UF,PN,BOP-2,3C3)	6SL3230-2YE26-0UF0	CONVERTER
G120X (400V,IP20,11kW,UF,DP,BOP-2,3C3)	6SL3230-2YE26-0UP0	CONVERTER
G120X (400V,IP20,11kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE26-1AB0	CONVERTER
G120X (400V,IP20,11kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE26-1AF0	CONVERTER
G120X (400V,IP20,11kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE26-1AP0	CONVERTER
G120X (400V,IP20,11kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE26-1UB0	CONVERTER
G120X (400V,IP20,11kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE26-1UF0	CONVERTER
G120X (400V,IP20,11kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE26-1UP0	CONVERTER
G120X (400V,IP20,15kW,C2,USS,BOP-2,3C3)	6SL3230-2YE28-0AB0	CONVERTER
G120X (400V,IP20,15kW,C2,PN,BOP-2,3C3)	6SL3230-2YE28-0AF0	CONVERTER
G120X (400V,IP20,15kW,C2,DP,BOP-2,3C3)	6SL3230-2YE28-0AP0	CONVERTER
G120X (400V,IP20,15kW,UF,USS,BOP-2,3C3)	6SL3230-2YE28-0UB0	CONVERTER
G120X (400V,IP20,15kW,UF,PN,BOP-2,3C3)	6SL3230-2YE28-0UF0	CONVERTER
G120X (400V,IP20,15kW,UF,DP,BOP-2,3C3)	6SL3230-2YE28-0UP0	CONVERTER
G120X (400V,IP20,15kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE28-1AB0	CONVERTER
G120X (400V,IP20,15kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE28-1AF0	CONVERTER
G120X (400V,IP20,15kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE28-1AP0	CONVERTER
G120X (400V,IP20,15kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE28-1UB0	CONVERTER
G120X (400V,IP20,15kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE28-1UF0	CONVERTER
G120X (400V,IP20,15kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE28-1UP0	CONVERTER
G120X (400V,IP20,18,5kW,C2,USS,BOP-2,3C3)	6SL3230-2YE30-0AB0	CONVERTER
G120X (400V,IP20,18,5kW,C2,PN,BOP-2,3C3)	6SL3230-2YE30-0AF0	CONVERTER
G120X (400V,IP20,18,5kW,C2,DP,BOP-2,3C3)	6SL3230-2YE30-0AP0	CONVERTER
G120X (400V,IP20,18,5kW,UF,USS,BOP-2,3C3)	6SL3230-2YE30-0UB0	CONVERTER

G120X (400V,IP20,18,5kW,UF,PN,BOP-2,3C3)	6SL3230-2YE30-0UF0	CONVERTER
G120X (400V,IP20,18,5kW,UF,DP,BOP-2,3C3)	6SL3230-2YE30-0UP0	CONVERTER
G120X (400V,IP20,18,5kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE30-1AB0	CONVERTER
G120X (400V,IP20,18,5kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE30-1AF0	CONVERTER
G120X (400V,IP20,18,5kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE30-1AP0	CONVERTER
G120X (400V,IP20,18,5kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE30-1UB0	CONVERTER
G120X (400V,IP20,18,5kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE30-1UF0	CONVERTER
G120X (400V,IP20,18,5kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE30-1UP0	CONVERTER
G120X (400V,IP20,22kW,C2,USS,BOP-2,3C3)	6SL3230-2YE32-0AB0	CONVERTER
G120X (400V,IP20,22kW,C2,PN,BOP-2,3C3)	6SL3230-2YE32-0AF0	CONVERTER
G120X (400V,IP20,22kW,C2,DP,BOP-2,3C3)	6SL3230-2YE32-0AP0	CONVERTER
G120X (400V,IP20,22kW,UF,USS,BOP-2,3C3)	6SL3230-2YE32-0UB0	CONVERTER
G120X (400V,IP20,22kW,UF,PN,BOP-2,3C3)	6SL3230-2YE32-0UF0	CONVERTER
G120X (400V,IP20,22kW,UF,DP,BOP-2,3C3)	6SL3230-2YE32-0UP0	CONVERTER
G120X (400V,IP20,22kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE32-1AB0	CONVERTER
G120X (400V,IP20,22kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE32-1AF0	CONVERTER
G120X (400V,IP20,22kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE32-1AP0	CONVERTER
G120X (400V,IP20,22kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE32-1UB0	CONVERTER
G120X (400V,IP20,22kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE32-1UF0	CONVERTER
G120X (400V,IP20,22kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE32-1UP0	CONVERTER
G120X (400V,IP20,30kW,C2,USS,BOP-2,3C3)	6SL3230-2YE34-0AB0	CONVERTER
G120X (400V,IP20,30kW,C2,PN,BOP-2,3C3)	6SL3230-2YE34-0AF0	CONVERTER
G120X (400V,IP20,30kW,C2,DP,BOP-2,3C3)	6SL3230-2YE34-0AP0	CONVERTER
G120X (400V,IP20,30kW,UF,USS,BOP-2,3C3)	6SL3230-2YE34-0UB0	CONVERTER
G120X (400V,IP20,30kW,UF,PN,BOP-2,3C3)	6SL3230-2YE34-0UF0	CONVERTER
G120X (400V,IP20,30kW,UF,DP,BOP-2,3C3)	6SL3230-2YE34-0UP0	CONVERTER
G120X (400V,IP20,30kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE34-1AB0	CONVERTER
G120X (400V,IP20,30kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE34-1AF0	CONVERTER
G120X (400V,IP20,30kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE34-1AP0	CONVERTER
G120X (400V,IP20,30kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE34-1UB0	CONVERTER
G120X (400V,IP20,30kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE34-1UF0	CONVERTER
G120X (400V,IP20,30kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE34-1UP0	CONVERTER
G120X (400V,IP20,37kW,C2,USS,BOP-2,3C3)	6SL3230-2YE36-0AB0	CONVERTER
G120X (400V,IP20,37kW,C2,PN,BOP-2,3C3)	6SL3230-2YE36-0AF0	CONVERTER
G120X (400V,IP20,37kW,C2,DP,BOP-2,3C3)	6SL3230-2YE36-0AP0	CONVERTER
G120X (400V,IP20,37kW,UF,USS,BOP-2,3C3)	6SL3230-2YE36-0UB0	CONVERTER
G120X (400V,IP20,37kW,UF,PN,BOP-2,3C3)	6SL3230-2YE36-0UF0	CONVERTER
G120X (400V,IP20,37kW,UF,DP,BOP-2,3C3)	6SL3230-2YE36-0UP0	CONVERTER
G120X (400V,IP20,37kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE36-1AB0	CONVERTER
G120X (400V,IP20,37kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE36-1AF0	CONVERTER
G120X (400V,IP20,37kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE36-1AP0	CONVERTER
G120X (400V,IP20,37kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE36-1UB0	CONVERTER
G120X (400V,IP20,37kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE36-1UF0	CONVERTER
G120X (400V,IP20,37kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE36-1UP0	CONVERTER

G120X (400V,IP20,45kW,C2,USS,BOP-2,3C3)	6SL3230-2YE38-0AB0	CONVERTER
G120X (400V,IP20,45kW,C2,PN,BOP-2,3C3)	6SL3230-2YE38-0AF0	CONVERTER
G120X (400V,IP20,45kW,C2,DP,BOP-2,3C3)	6SL3230-2YE38-0AP0	CONVERTER
G120X (400V,IP20,45kW,UF,USS,BOP-2,3C3)	6SL3230-2YE38-0UB0	CONVERTER
G120X (400V,IP20,45kW,UF,PN,BOP-2,3C3)	6SL3230-2YE38-0UF0	CONVERTER
G120X (400V,IP20,45kW,UF,DP,BOP-2,3C3)	6SL3230-2YE38-0UP0	CONVERTER
G120X (400V,IP20,45kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE38-1AB0	CONVERTER
G120X (400V,IP20,45kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE38-1AF0	CONVERTER
G120X (400V,IP20,45kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE38-1AP0	CONVERTER
G120X (400V,IP20,45kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE38-1UB0	CONVERTER
G120X (400V,IP20,45kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE38-1UF0	CONVERTER
G120X (400V,IP20,45kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE38-1UP0	CONVERTER
G120X (400V,IP20,55kW,C2,USS,BOP-2,3C3)	6SL3230-2YE40-0AB0	CONVERTER
G120X (400V,IP20,55kW,C2,PN,BOP-2,3C3)	6SL3230-2YE40-0AF0	CONVERTER
G120X (400V,IP20,55kW,C2,DP,BOP-2,3C3)	6SL3230-2YE40-0AP0	CONVERTER
G120X (400V,IP20,55kW,UF,USS,BOP-2,3C3)	6SL3230-2YE40-0UB0	CONVERTER
G120X (400V,IP20,55kW,UF,PN,BOP-2,3C3)	6SL3230-2YE40-0UF0	CONVERTER
G120X (400V,IP20,55kW,UF,DP,BOP-2,3C3)	6SL3230-2YE40-0UP0	CONVERTER
G120X (400V,IP20,55kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE40-1AB0	CONVERTER
G120X (400V,IP20,55kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE40-1AF0	CONVERTER
G120X (400V,IP20,55kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE40-1AP0	CONVERTER
G120X (400V,IP20,55kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE40-1UB0	CONVERTER
G120X (400V,IP20,55kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE40-1UF0	CONVERTER
G120X (400V,IP20,55kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE40-1UP0	CONVERTER
G120X (400V,IP20,75kW,C2,USS,BOP-2,3C3)	6SL3230-2YE42-0AB0	CONVERTER
G120X (400V,IP20,75kW,C2,PN,BOP-2,3C3)	6SL3230-2YE42-0AF0	CONVERTER
G120X (400V,IP20,75kW,C2,DP,BOP-2,3C3)	6SL3230-2YE42-0AP0	CONVERTER
G120X (400V,IP20,75kW,UF,USS,BOP-2,3C3)	6SL3230-2YE42-0UB0	CONVERTER
G120X (400V,IP20,75kW,UF,PN,BOP-2,3C3)	6SL3230-2YE42-0UF0	CONVERTER
G120X (400V,IP20,75kW,UF,DP,BOP-2,3C3)	6SL3230-2YE42-0UP0	CONVERTER
G120X (400V,IP20,75kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE42-1AB0	CONVERTER
G120X (400V,IP20,75kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE42-1AF0	CONVERTER
G120X (400V,IP20,75kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE42-1AP0	CONVERTER
G120X (400V,IP20,75kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE42-1UB0	CONVERTER
G120X (400V,IP20,75kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE42-1UF0	CONVERTER
G120X (400V,IP20,75kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE42-1UP0	CONVERTER
G120X (400V,IP20,90kW,C2,USS,BOP-2,3C3)	6SL3230-2YE44-0AB0	CONVERTER
G120X (400V,IP20,90kW,C2,PN,BOP-2,3C3)	6SL3230-2YE44-0AF0	CONVERTER
G120X (400V,IP20,90kW,C2,DP,BOP-2,3C3)	6SL3230-2YE44-0AP0	CONVERTER
G120X (400V,IP20,90kW,UF,USS,BOP-2,3C3)	6SL3230-2YE44-0UB0	CONVERTER
G120X (400V,IP20,90kW,UF,PN,BOP-2,3C3)	6SL3230-2YE44-0UF0	CONVERTER
G120X (400V,IP20,90kW,UF,DP,BOP-2,3C3)	6SL3230-2YE44-0UP0	CONVERTER
G120X (400V,IP20,90kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE44-1AB0	CONVERTER
G120X (400V,IP20,90kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE44-1AF0	CONVERTER

G120X (400V,IP20,90kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE44-1AP0	CONVERTER
G120X (400V,IP20,90kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE44-1UB0	CONVERTER
G120X (400V,IP20,90kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE44-1UF0	CONVERTER
G120X (400V,IP20,90kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE44-1UP0	CONVERTER
G120X (400V,IP20,110kW,C2,USS,BOP-2,3C3)	6SL3230-2YE46-0AB0	CONVERTER
G120X (400V,IP20,110kW,C2,PN,BOP-2,3C3)	6SL3230-2YE46-0AF0	CONVERTER
G120X (400V,IP20,110kW,C2,DP,BOP-2,3C3)	6SL3230-2YE46-0AP0	CONVERTER
G120X (400V,IP20,110kW,UF,USS,BOP-2,3C3)	6SL3230-2YE46-0UB0	CONVERTER
G120X (400V,IP20,110kW,UF,PN,BOP-2,3C3)	6SL3230-2YE46-0UF0	CONVERTER
G120X (400V,IP20,110kW,UF,DP,BOP-2,3C3)	6SL3230-2YE46-0UP0	CONVERTER
G120X (400V,IP20,110kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE46-1AB0	CONVERTER
G120X (400V,IP20,110kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE46-1AF0	CONVERTER
G120X (400V,IP20,110kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE46-1AP0	CONVERTER
G120X (400V,IP20,110kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE46-1UB0	CONVERTER
G120X (400V,IP20,110kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE46-1UF0	CONVERTER
G120X (400V,IP20,110kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE46-1UP0	CONVERTER
G120X (400V,IP20,132kW,C2,USS,BOP-2,3C3)	6SL3230-2YE48-0AB0	CONVERTER
G120X (400V,IP20,132kW,C2,PN,BOP-2,3C3)	6SL3230-2YE48-0AF0	CONVERTER
G120X (400V,IP20,132kW,C2,DP,BOP-2,3C3)	6SL3230-2YE48-0AP0	CONVERTER
G120X (400V,IP20,132kW,UF,USS,BOP-2,3C3)	6SL3230-2YE48-0UB0	CONVERTER
G120X (400V,IP20,132kW,UF,PN,BOP-2,3C3)	6SL3230-2YE48-0UF0	CONVERTER
G120X (400V,IP20,132kW,UF,DP,BOP-2,3C3)	6SL3230-2YE48-0UP0	CONVERTER
G120X (400V,IP20,132kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE48-1AB0	CONVERTER
G120X (400V,IP20,132kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE48-1AF0	CONVERTER
G120X (400V,IP20,132kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE48-1AP0	CONVERTER
G120X (400V,IP20,132kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YE48-1UB0	CONVERTER
G120X (400V,IP20,132kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YE48-1UF0	CONVERTER
G120X (400V,IP20,132kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YE48-1UP0	CONVERTER
G120X (400V,IP20,160kW,C2,USS,BOP-2,3C3)	6SL3230-2YE50-0AB0	CONVERTER
G120X (400V,IP20,160kW,C2,PN,BOP-2,3C3)	6SL3230-2YE50-0AF0	CONVERTER
G120X (400V,IP20,160kW,C2,DP,BOP-2,3C3)	6SL3230-2YE50-0AP0	CONVERTER
G120X (400V,IP20,160kW,C3,USS,BOP-2,3C3)	6SL3230-2YE50-0CB0	CONVERTER
G120X (400V,IP20,160kW,C3,PN,BOP-2,3C3)	6SL3230-2YE50-0CF0	CONVERTER
G120X (400V,IP20,160kW,C3,DP,BOP-2,3C3)	6SL3230-2YE50-0CP0	CONVERTER
G120X (400V,IP20,160kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE50-1AB0	CONVERTER
G120X (400V,IP20,160kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE50-1AF0	CONVERTER
G120X (400V,IP20,160kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE50-1AP0	CONVERTER
G120X (400V,IP20,160kW,C3,USS,BOP-2,3C3,IO)	6SL3230-2YE50-1CB0	CONVERTER
G120X (400V,IP20,160kW,C3,PN,BOP-2,3C3,IO)	6SL3230-2YE50-1CF0	CONVERTER
G120X (400V,IP20,160kW,C3,DP,BOP-2,3C3,IO)	6SL3230-2YE50-1CP0	CONVERTER
G120X (400V,IP20,200kW,C2,USS,BOP-2,3C3)	6SL3230-2YE52-0AB0	CONVERTER
G120X (400V,IP20,200kW,C2,PN,BOP-2,3C3)	6SL3230-2YE52-0AF0	CONVERTER
G120X (400V,IP20,200kW,C2,DP,BOP-2,3C3)	6SL3230-2YE52-0AP0	CONVERTER
G120X (400V,IP20,200kW,C3,USS,BOP-2,3C3)	6SL3230-2YE52-0CB0	CONVERTER

G120X (400V,IP20,200kW,C3,PN,BOP-2,3C3)	6SL3230-2YE52-0CF0	CONVERTER
G120X (400V,IP20,200kW,C3,DP,BOP-2,3C3)	6SL3230-2YE52-0CP0	CONVERTER
G120X (400V,IP20,200kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE52-1AB0	CONVERTER
G120X (400V,IP20,200kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE52-1AF0	CONVERTER
G120X (400V,IP20,200kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE52-1AP0	CONVERTER
G120X (400V,IP20,200kW,C3,USS,BOP-2,3C3,IO)	6SL3230-2YE52-1CB0	CONVERTER
G120X (400V,IP20,200kW,C3,PN,BOP-2,3C3,IO)	6SL3230-2YE52-1CF0	CONVERTER
G120X (400V,IP20,200kW,C3,DP,BOP-2,3C3,IO)	6SL3230-2YE52-1CP0	CONVERTER
G120X (400V,IP20,250kW,C2,USS,BOP-2,3C3)	6SL3230-2YE54-0AB0	CONVERTER
G120X (400V,IP20,250kW,C2,PN,BOP-2,3C3)	6SL3230-2YE54-0AF0	CONVERTER
G120X (400V,IP20,250kW,C2,DP,BOP-2,3C3)	6SL3230-2YE54-0AP0	CONVERTER
G120X (400V,IP20,250kW,C3,USS,BOP-2,3C3)	6SL3230-2YE54-0CB0	CONVERTER
G120X (400V,IP20,250kW,C3,PN,BOP-2,3C3)	6SL3230-2YE54-0CF0	CONVERTER
G120X (400V,IP20,250kW,C3,DP,BOP-2,3C3)	6SL3230-2YE54-0CP0	CONVERTER
G120X (400V,IP20,250kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YE54-1AB0	CONVERTER
G120X (400V,IP20,250kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YE54-1AF0	CONVERTER
G120X (400V,IP20,250kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YE54-1AP0	CONVERTER
G120X (400V,IP20,250kW,C3,USS,BOP-2,3C3,IO)	6SL3230-2YE54-1CB0	CONVERTER
G120X (400V,IP20,250kW,C3,PN,BOP-2,3C3,IO)	6SL3230-2YE54-1CF0	CONVERTER
G120X (400V,IP20,250kW,C3,DP,BOP-2,3C3,IO)	6SL3230-2YE54-1CP0	CONVERTER
G120X (690V,IP20,3kW,C2,USS,BOP-2,3C3)	6SL3230-2YH18-0AB0	CONVERTER
G120X (690V,IP20,3kW,C2,PN,BOP-2,3C3)	6SL3230-2YH18-0AF0	CONVERTER
G120X (690V,IP20,3kW,C2,DP,BOP-2,3C3)	6SL3230-2YH18-0AP0	CONVERTER
G120X (690V,IP20,3kW,UF,USS,BOP-2,3C3)	6SL3230-2YH18-0UB0	CONVERTER
G120X (690V,IP20,3kW,UF,PN,BOP-2,3C3)	6SL3230-2YH18-0UF0	CONVERTER
G120X (690V,IP20,3kW,UF,DP,BOP-2,3C3)	6SL3230-2YH18-0UP0	CONVERTER
G120X (690V,IP20,3kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YH18-1AB0	CONVERTER
G120X (690V,IP20,3kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YH18-1AF0	CONVERTER
G120X (690V,IP20,3kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YH18-1AP0	CONVERTER
G120X (690V,IP20,3kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH18-1UB0	CONVERTER
G120X (690V,IP20,3kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH18-1UF0	CONVERTER
G120X (690V,IP20,3kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH18-1UP0	CONVERTER
G120X (690V,IP20,4kW,C2,USS,BOP-2,3C3)	6SL3230-2YH20-0AB0	CONVERTER
G120X (690V,IP20,4kW,C2,PN,BOP-2,3C3)	6SL3230-2YH20-0AF0	CONVERTER
G120X (690V,IP20,4kW,C2,DP,BOP-2,3C3)	6SL3230-2YH20-0AP0	CONVERTER
G120X (690V,IP20,4kW,UF,USS,BOP-2,3C3)	6SL3230-2YH20-0UB0	CONVERTER
G120X (690V,IP20,4kW,UF,PN,BOP-2,3C3)	6SL3230-2YH20-0UF0	CONVERTER
G120X (690V,IP20,4kW,UF,DP,BOP-2,3C3)	6SL3230-2YH20-0UP0	CONVERTER
G120X (690V,IP20,4kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YH20-1AB0	CONVERTER
G120X (690V,IP20,4kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YH20-1AF0	CONVERTER
G120X (690V,IP20,4kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YH20-1AP0	CONVERTER
G120X (690V,IP20,4kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH20-1UB0	CONVERTER
G120X (690V,IP20,4kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH20-1UF0	CONVERTER
G120X (690V,IP20,4kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH20-1UP0	CONVERTER

G120X (690V,IP20,5.5kW,C2,USS,BOP-2,3C3)	6SL3230-2YH22-0AB0	CONVERTER
G120X (690V,IP20,5.5kW,C2,PN,BOP-2,3C3)	6SL3230-2YH22-0AF0	CONVERTER
G120X (690V,IP20,5.5kW,C2,DP,BOP-2,3C3)	6SL3230-2YH22-0AP0	CONVERTER
G120X (690V,IP20,5.5kW,UF,USS,BOP-2,3C3)	6SL3230-2YH22-0UB0	CONVERTER
G120X (690V,IP20,5.5kW,UF,PN,BOP-2,3C3)	6SL3230-2YH22-0UF0	CONVERTER
G120X (690V,IP20,5.5kW,UF,DP,BOP-2,3C3)	6SL3230-2YH22-0UP0	CONVERTER
G120X (690V,IP20,5.5kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YH22-1AB0	CONVERTER
G120X (690V,IP20,5.5kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YH22-1AF0	CONVERTER
G120X (690V,IP20,5.5kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YH22-1AP0	CONVERTER
G120X (690V,IP20,5.5kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH22-1UB0	CONVERTER
G120X (690V,IP20,5.5kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH22-1UF0	CONVERTER
G120X (690V,IP20,5.5kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH22-1UP0	CONVERTER
G120X (690V,IP20,7.5kW,C2,USS,BOP-2,3C3)	6SL3230-2YH24-0AB0	CONVERTER
G120X (690V,IP20,7.5kW,C2,PN,BOP-2,3C3)	6SL3230-2YH24-0AF0	CONVERTER
G120X (690V,IP20,7.5kW,C2,DP,BOP-2,3C3)	6SL3230-2YH24-0AP0	CONVERTER
G120X (690V,IP20,7.5kW,UF,USS,BOP-2,3C3)	6SL3230-2YH24-0UB0	CONVERTER
G120X (690V,IP20,7.5kW,UF,PN,BOP-2,3C3)	6SL3230-2YH24-0UF0	CONVERTER
G120X (690V,IP20,7.5kW,UF,DP,BOP-2,3C3)	6SL3230-2YH24-0UP0	CONVERTER
G120X (690V,IP20,7.5kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YH24-1AB0	CONVERTER
G120X (690V,IP20,7.5kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YH24-1AF0	CONVERTER
G120X (690V,IP20,7.5kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YH24-1AP0	CONVERTER
G120X (690V,IP20,7.5kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH24-1UB0	CONVERTER
G120X (690V,IP20,7.5kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH24-1UF0	CONVERTER
G120X (690V,IP20,7.5kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH24-1UP0	CONVERTER
G120X (690V,IP20,11kW,C2,USS,BOP-2,3C3)	6SL3230-2YH26-0AB0	CONVERTER
G120X (690V,IP20,11kW,C2,PN,BOP-2,3C3)	6SL3230-2YH26-0AF0	CONVERTER
G120X (690V,IP20,11kW,C2,DP,BOP-2,3C3)	6SL3230-2YH26-0AP0	CONVERTER
G120X (690V,IP20,11kW,UF,USS,BOP-2,3C3)	6SL3230-2YH26-0UB0	CONVERTER
G120X (690V,IP20,11kW,UF,PN,BOP-2,3C3)	6SL3230-2YH26-0UF0	CONVERTER
G120X (690V,IP20,11kW,UF,DP,BOP-2,3C3)	6SL3230-2YH26-0UP0	CONVERTER
G120X (690V,IP20,11kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YH26-1AB0	CONVERTER
G120X (690V,IP20,11kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YH26-1AF0	CONVERTER
G120X (690V,IP20,11kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YH26-1AP0	CONVERTER
G120X (690V,IP20,11kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH26-1UB0	CONVERTER
G120X (690V,IP20,11kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH26-1UF0	CONVERTER
G120X (690V,IP20,11kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH26-1UP0	CONVERTER
G120X (690V,IP20,15kW,C2,USS,BOP-2,3C3)	6SL3230-2YH28-0AB0	CONVERTER
G120X (690V,IP20,15kW,C2,PN,BOP-2,3C3)	6SL3230-2YH28-0AF0	CONVERTER
G120X (690V,IP20,15kW,C2,DP,BOP-2,3C3)	6SL3230-2YH28-0AP0	CONVERTER
G120X (690V,IP20,15kW,UF,USS,BOP-2,3C3)	6SL3230-2YH28-0UB0	CONVERTER
G120X (690V,IP20,15kW,UF,PN,BOP-2,3C3)	6SL3230-2YH28-0UF0	CONVERTER
G120X (690V,IP20,15kW,UF,DP,BOP-2,3C3)	6SL3230-2YH28-0UP0	CONVERTER
G120X (690V,IP20,15kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YH28-1AB0	CONVERTER
G120X (690V,IP20,15kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YH28-1AF0	CONVERTER

G120X (690V,IP20,15kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YH28-1AP0	CONVERTER
G120X (690V,IP20,15kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH28-1UB0	CONVERTER
G120X (690V,IP20,15kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH28-1UF0	CONVERTER
G120X (690V,IP20,15kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH28-1UP0	CONVERTER
G120X (690V,IP20,18,5kW,C2,USS,BOP-2,3C3)	6SL3230-2YH30-0AB0	CONVERTER
G120X (690V,IP20,18,5kW,C2,PN,BOP-2,3C3)	6SL3230-2YH30-0AF0	CONVERTER
G120X (690V,IP20,18,5kW,C2,DP,BOP-2,3C3)	6SL3230-2YH30-0AP0	CONVERTER
G120X (690V,IP20,18,5kW,UF,USS,BOP-2,3C3)	6SL3230-2YH30-0UB0	CONVERTER
G120X (690V,IP20,18,5kW,UF,PN,BOP-2,3C3)	6SL3230-2YH30-0UF0	CONVERTER
G120X (690V,IP20,18,5kW,UF,DP,BOP-2,3C3)	6SL3230-2YH30-0UP0	CONVERTER
G120X (690V,IP20,18,5kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YH30-1AB0	CONVERTER
G120X (690V,IP20,18,5kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YH30-1AF0	CONVERTER
G120X (690V,IP20,18,5kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YH30-1AP0	CONVERTER
G120X (690V,IP20,18,5kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH30-1UB0	CONVERTER
G120X (690V,IP20,18,5kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH30-1UF0	CONVERTER
G120X (690V,IP20,18,5kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH30-1UP0	CONVERTER
G120X (690V,IP20,22kW,C2,USS,BOP-2,3C3)	6SL3230-2YH32-0AB0	CONVERTER
G120X (690V,IP20,22kW,C2,PN,BOP-2,3C3)	6SL3230-2YH32-0AF0	CONVERTER
G120X (690V,IP20,22kW,C2,DP,BOP-2,3C3)	6SL3230-2YH32-0AP0	CONVERTER
G120X (690V,IP20,22kW,UF,USS,BOP-2,3C3)	6SL3230-2YH32-0UB0	CONVERTER
G120X (690V,IP20,22kW,UF,PN,BOP-2,3C3)	6SL3230-2YH32-0UF0	CONVERTER
G120X (690V,IP20,22kW,UF,DP,BOP-2,3C3)	6SL3230-2YH32-0UP0	CONVERTER
G120X (690V,IP20,22kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YH32-1AB0	CONVERTER
G120X (690V,IP20,22kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YH32-1AF0	CONVERTER
G120X (690V,IP20,22kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YH32-1AP0	CONVERTER
G120X (690V,IP20,22kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH32-1UB0	CONVERTER
G120X (690V,IP20,22kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH32-1UF0	CONVERTER
G120X (690V,IP20,22kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH32-1UP0	CONVERTER
G120X (690V,IP20,30kW,C2,USS,BOP-2,3C3)	6SL3230-2YH34-0AB0	CONVERTER
G120X (690V,IP20,30kW,C2,PN,BOP-2,3C3)	6SL3230-2YH34-0AF0	CONVERTER
G120X (690V,IP20,30kW,C2,DP,BOP-2,3C3)	6SL3230-2YH34-0AP0	CONVERTER
G120X (690V,IP20,30kW,UF,USS,BOP-2,3C3)	6SL3230-2YH34-0UB0	CONVERTER
G120X (690V,IP20,30kW,UF,PN,BOP-2,3C3)	6SL3230-2YH34-0UF0	CONVERTER
G120X (690V,IP20,30kW,UF,DP,BOP-2,3C3)	6SL3230-2YH34-0UP0	CONVERTER
G120X (690V,IP20,30kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YH34-1AB0	CONVERTER
G120X (690V,IP20,30kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YH34-1AF0	CONVERTER
G120X (690V,IP20,30kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YH34-1AP0	CONVERTER
G120X (690V,IP20,30kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH34-1UB0	CONVERTER
G120X (690V,IP20,30kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH34-1UF0	CONVERTER
G120X (690V,IP20,30kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH34-1UP0	CONVERTER
G120X (690V,IP20,37kW,C2,USS,BOP-2,3C3)	6SL3230-2YH36-0AB0	CONVERTER
G120X (690V,IP20,37kW,C2,PN,BOP-2,3C3)	6SL3230-2YH36-0AF0	CONVERTER
G120X (690V,IP20,37kW,C2,DP,BOP-2,3C3)	6SL3230-2YH36-0AP0	CONVERTER
G120X (690V,IP20,37kW,UF,USS,BOP-2,3C3)	6SL3230-2YH36-0UB0	CONVERTER

G120X (690V,IP20,37kW,UF,PN,BOP-2,3C3)	6SL3230-2YH36-0UF0	CONVERTER
G120X (690V,IP20,37kW,UF,DP,BOP-2,3C3)	6SL3230-2YH36-0UP0	CONVERTER
G120X (690V,IP20,37kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YH36-1AB0	CONVERTER
G120X (690V,IP20,37kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YH36-1AF0	CONVERTER
G120X (690V,IP20,37kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YH36-1AP0	CONVERTER
G120X (690V,IP20,37kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH36-1UB0	CONVERTER
G120X (690V,IP20,37kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH36-1UF0	CONVERTER
G120X (690V,IP20,37kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH36-1UP0	CONVERTER
G120X (690V,IP20,45kW,C2,USS,BOP-2,3C3)	6SL3230-2YH38-0AB0	CONVERTER
G120X (690V,IP20,45kW,C2,PN,BOP-2,3C3)	6SL3230-2YH38-0AF0	CONVERTER
G120X (690V,IP20,45kW,C2,DP,BOP-2,3C3)	6SL3230-2YH38-0AP0	CONVERTER
G120X (690V,IP20,45kW,UF,USS,BOP-2,3C3)	6SL3230-2YH38-0UB0	CONVERTER
G120X (690V,IP20,45kW,UF,PN,BOP-2,3C3)	6SL3230-2YH38-0UF0	CONVERTER
G120X (690V,IP20,45kW,UF,DP,BOP-2,3C3)	6SL3230-2YH38-0UP0	CONVERTER
G120X (690V,IP20,45kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YH38-1AB0	CONVERTER
G120X (690V,IP20,45kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YH38-1AF0	CONVERTER
G120X (690V,IP20,45kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YH38-1AP0	CONVERTER
G120X (690V,IP20,45kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH38-1UB0	CONVERTER
G120X (690V,IP20,45kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH38-1UF0	CONVERTER
G120X (690V,IP20,45kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH38-1UP0	CONVERTER
G120X (690V,IP20,55kW,C2,USS,BOP-2,3C3)	6SL3230-2YH40-0AB0	CONVERTER
G120X (690V,IP20,55kW,C2,PN,BOP-2,3C3)	6SL3230-2YH40-0AF0	CONVERTER
G120X (690V,IP20,55kW,C2,DP,BOP-2,3C3)	6SL3230-2YH40-0AP0	CONVERTER
G120X (690V,IP20,55kW,UF,USS,BOP-2,3C3)	6SL3230-2YH40-0UB0	CONVERTER
G120X (690V,IP20,55kW,UF,PN,BOP-2,3C3)	6SL3230-2YH40-0UF0	CONVERTER
G120X (690V,IP20,55kW,UF,DP,BOP-2,3C3)	6SL3230-2YH40-0UP0	CONVERTER
G120X (690V,IP20,55kW,C2,USS,BOP-2,3C3,IO)	6SL3230-2YH40-1AB0	CONVERTER
G120X (690V,IP20,55kW,C2,PN,BOP-2,3C3,IO)	6SL3230-2YH40-1AF0	CONVERTER
G120X (690V,IP20,55kW,C2,DP,BOP-2,3C3,IO)	6SL3230-2YH40-1AP0	CONVERTER
G120X (690V,IP20,55kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH40-1UB0	CONVERTER
G120X (690V,IP20,55kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH40-1UF0	CONVERTER
G120X (690V,IP20,55kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH40-1UP0	CONVERTER
G120X (690V,IP20,75kW,C3,USS,BOP-2,3C3)	6SL3230-2YH42-0CB0	CONVERTER
G120X (690V,IP20,75kW,C3,PN,BOP-2,3C3)	6SL3230-2YH42-0CF0	CONVERTER
G120X (690V,IP20,75kW,C3,DP,BOP-2,3C3)	6SL3230-2YH42-0CP0	CONVERTER
G120X (690V,IP20,75kW,UF,USS,BOP-2,3C3)	6SL3230-2YH42-0UB0	CONVERTER
G120X (690V,IP20,75kW,UF,PN,BOP-2,3C3)	6SL3230-2YH42-0UF0	CONVERTER
G120X (690V,IP20,75kW,UF,DP,BOP-2,3C3)	6SL3230-2YH42-0UP0	CONVERTER
G120X (690V,IP20,75kW,C3,USS,BOP-2,3C3,IO)	6SL3230-2YH42-1CB0	CONVERTER
G120X (690V,IP20,75kW,C3,PN,BOP-2,3C3,IO)	6SL3230-2YH42-1CF0	CONVERTER
G120X (690V,IP20,75kW,C3,DP,BOP-2,3C3,IO)	6SL3230-2YH42-1CP0	CONVERTER
G120X (690V,IP20,75kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH42-1UB0	CONVERTER
G120X (690V,IP20,75kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH42-1UF0	CONVERTER
G120X (690V,IP20,75kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH42-1UP0	CONVERTER

G120X (690V,IP20,90kW,C3,USS,BOP-2,3C3)	6SL3230-2YH44-0CB0	CONVERTER
G120X (690V,IP20,90kW,C3,PN,BOP-2,3C3)	6SL3230-2YH44-0CF0	CONVERTER
G120X (690V,IP20,90kW,C3,DP,BOP-2,3C3)	6SL3230-2YH44-0CP0	CONVERTER
G120X (690V,IP20,90kW,UF,USS,BOP-2,3C3)	6SL3230-2YH44-0UB0	CONVERTER
G120X (690V,IP20,90kW,UF,PN,BOP-2,3C3)	6SL3230-2YH44-0UF0	CONVERTER
G120X (690V,IP20,90kW,UF,DP,BOP-2,3C3)	6SL3230-2YH44-0UP0	CONVERTER
G120X (690V,IP20,90kW,C3,USS,BOP-2,3C3,IO)	6SL3230-2YH44-1CB0	CONVERTER
G120X (690V,IP20,90kW,C3,PN,BOP-2,3C3,IO)	6SL3230-2YH44-1CF0	CONVERTER
G120X (690V,IP20,90kW,C3,DP,BOP-2,3C3,IO)	6SL3230-2YH44-1CP0	CONVERTER
G120X (690V,IP20,90kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH44-1UB0	CONVERTER
G120X (690V,IP20,90kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH44-1UF0	CONVERTER
G120X (690V,IP20,90kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH44-1UP0	CONVERTER
G120X (690V,IP20,110kW,C3,USS,BOP-2,3C3)	6SL3230-2YH46-0CB0	CONVERTER
G120X (690V,IP20,110kW,C3,PN,BOP-2,3C3)	6SL3230-2YH46-0CF0	CONVERTER
G120X (690V,IP20,110kW,C3,DP,BOP-2,3C3)	6SL3230-2YH46-0CP0	CONVERTER
G120X (690V,IP20,110kW,UF,USS,BOP-2,3C3)	6SL3230-2YH46-0UB0	CONVERTER
G120X (690V,IP20,110kW,UF,PN,BOP-2,3C3)	6SL3230-2YH46-0UF0	CONVERTER
G120X (690V,IP20,110kW,UF,DP,BOP-2,3C3)	6SL3230-2YH46-0UP0	CONVERTER
G120X (690V,IP20,110kW,C3,USS,BOP-2,3C3,IO)	6SL3230-2YH46-1CB0	CONVERTER
G120X (690V,IP20,110kW,C3,PN,BOP-2,3C3,IO)	6SL3230-2YH46-1CF0	CONVERTER
G120X (690V,IP20,110kW,C3,DP,BOP-2,3C3,IO)	6SL3230-2YH46-1CP0	CONVERTER
G120X (690V,IP20,110kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH46-1UB0	CONVERTER
G120X (690V,IP20,110kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH46-1UF0	CONVERTER
G120X (690V,IP20,110kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH46-1UP0	CONVERTER
G120X (690V,IP20,132kW,C3,USS,BOP-2,3C3)	6SL3230-2YH48-0CB0	CONVERTER
G120X (690V,IP20,132kW,C3,PN,BOP-2,3C3)	6SL3230-2YH48-0CF0	CONVERTER
G120X (690V,IP20,132kW,C3,DP,BOP-2,3C3)	6SL3230-2YH48-0CP0	CONVERTER
G120X (690V,IP20,132kW,UF,USS,BOP-2,3C3)	6SL3230-2YH48-0UB0	CONVERTER
G120X (690V,IP20,132kW,UF,PN,BOP-2,3C3)	6SL3230-2YH48-0UF0	CONVERTER
G120X (690V,IP20,132kW,UF,DP,BOP-2,3C3)	6SL3230-2YH48-0UP0	CONVERTER
G120X (690V,IP20,132kW,C3,USS,BOP-2,3C3,IO)	6SL3230-2YH48-1CB0	CONVERTER
G120X (690V,IP20,132kW,C3,PN,BOP-2,3C3,IO)	6SL3230-2YH48-1CF0	CONVERTER
G120X (690V,IP20,132kW,C3,DP,BOP-2,3C3,IO)	6SL3230-2YH48-1CP0	CONVERTER
G120X (690V,IP20,132kW,UF,USS,BOP-2,3C3,IO)	6SL3230-2YH48-1UB0	CONVERTER
G120X (690V,IP20,132kW,UF,PN,BOP-2,3C3,IO)	6SL3230-2YH48-1UF0	CONVERTER
G120X (690V,IP20,132kW,UF,DP,BOP-2,3C3,IO)	6SL3230-2YH48-1UP0	CONVERTER
G120X (690V,IP20,160kW,C3,USS,BOP-2,3C3)	6SL3230-2YH50-0CB0	CONVERTER
G120X (690V,IP20,160kW,C3,PN,BOP-2,3C3)	6SL3230-2YH50-0CF0	CONVERTER
G120X (690V,IP20,160kW,C3,DP,BOP-2,3C3)	6SL3230-2YH50-0CP0	CONVERTER
G120X (690V,IP20,160kW,C3,USS,BOP-2,3C3,IO)	6SL3230-2YH50-1CB0	CONVERTER
G120X (690V,IP20,160kW,C3,PN,BOP-2,3C3,IO)	6SL3230-2YH50-1CF0	CONVERTER
G120X (690V,IP20,160kW,C3,DP,BOP-2,3C3,IO)	6SL3230-2YH50-1CP0	CONVERTER
G120X (690V,IP20,200kW,C3,USS,BOP-2,3C3)	6SL3230-2YH52-0CB0	CONVERTER
G120X (690V,IP20,200kW,C3,PN,BOP-2,3C3)	6SL3230-2YH52-0CF0	CONVERTER

G120X (690V,IP20,200kW,C3,DP,BOP-2,3C3)	6SL3230-2YH52-0CP0	CONVERTER
G120X (690V,IP20,200kW,C3,USS,BOP-2,3C3,IO)	6SL3230-2YH52-1CB0	CONVERTER
G120X (690V,IP20,200kW,C3,PN,BOP-2,3C3,IO)	6SL3230-2YH52-1CF0	CONVERTER
G120X (690V,IP20,200kW,C3,DP,BOP-2,3C3,IO)	6SL3230-2YH52-1CP0	CONVERTER
G120X (690V,IP20,250kW,C3,USS,BOP-2,3C3)	6SL3230-2YH54-0CB0	CONVERTER
G120X (690V,IP20,250kW,C3,PN,BOP-2,3C3)	6SL3230-2YH54-0CF0	CONVERTER
G120X (690V,IP20,250kW,C3,DP,BOP-2,3C3)	6SL3230-2YH54-0CP0	CONVERTER
G120X (690V,IP20,250kW,C3,USS,BOP-2,3C3,IO)	6SL3230-2YH54-1CB0	CONVERTER
G120X (690V,IP20,250kW,C3,PN,BOP-2,3C3,IO)	6SL3230-2YH54-1CF0	CONVERTER
G120X (690V,IP20,250kW,C3,DP,BOP-2,3C3,IO)	6SL3230-2YH54-1CP0	CONVERTER
G120X (230V,IP20,0.75kW,UF,USS,IOP-2,3C3)	6SL3230-3YC10-0UB0	CONVERTER
G120X (230V,IP20,0.75kW,UF,PN,IOP-2,3C3)	6SL3230-3YC10-0UF0	CONVERTER
G120X (230V,IP20,0.75kW,UF,DP,IOP-2,3C3)	6SL3230-3YC10-0UP0	CONVERTER
G120X (230V,IP20,0.75kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC10-1UB0	CONVERTER
G120X (230V,IP20,0.75kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC10-1UF0	CONVERTER
G120X (230V,IP20,0.75kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC10-1UP0	CONVERTER
G120X (230V,IP20,1.1kW,UF,USS,IOP-2,3C3)	6SL3230-3YC12-0UB0	CONVERTER
G120X (230V,IP20,1.1kW,UF,PN,IOP-2,3C3)	6SL3230-3YC12-0UF0	CONVERTER
G120X (230V,IP20,1.1kW,UF,DP,IOP-2,3C3)	6SL3230-3YC12-0UP0	CONVERTER
G120X (230V,IP20,1.1kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC12-1UB0	CONVERTER
G120X (230V,IP20,1.1kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC12-1UF0	CONVERTER
G120X (230V,IP20,1.1kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC12-1UP0	CONVERTER
G120X (230V,IP20,1.5kW,UF,USS,IOP-2,3C3)	6SL3230-3YC14-0UB0	CONVERTER
G120X (230V,IP20,1.5kW,UF,PN,IOP-2,3C3)	6SL3230-3YC14-0UF0	CONVERTER
G120X (230V,IP20,1.5kW,UF,DP,IOP-2,3C3)	6SL3230-3YC14-0UP0	CONVERTER
G120X (230V,IP20,1.5kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC14-1UB0	CONVERTER
G120X (230V,IP20,1.5kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC14-1UF0	CONVERTER
G120X (230V,IP20,1.5kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC14-1UP0	CONVERTER
G120X (230V,IP20,2.2kW,UF,USS,IOP-2,3C3)	6SL3230-3YC16-0UB0	CONVERTER
G120X (230V,IP20,2.2kW,UF,PN,IOP-2,3C3)	6SL3230-3YC16-0UF0	CONVERTER
G120X (230V,IP20,2.2kW,UF,DP,IOP-2,3C3)	6SL3230-3YC16-0UP0	CONVERTER
G120X (230V,IP20,2.2kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC16-1UB0	CONVERTER
G120X (230V,IP20,2.2kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC16-1UF0	CONVERTER
G120X (230V,IP20,2.2kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC16-1UP0	CONVERTER
G120X (230V,IP20,3kW,UF,USS,IOP-2,3C3)	6SL3230-3YC18-0UB0	CONVERTER
G120X (230V,IP20,3kW,UF,PN,IOP-2,3C3)	6SL3230-3YC18-0UF0	CONVERTER
G120X (230V,IP20,3kW,UF,DP,IOP-2,3C3)	6SL3230-3YC18-0UP0	CONVERTER
G120X (230V,IP20,3kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC18-1UB0	CONVERTER
G120X (230V,IP20,3kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC18-1UF0	CONVERTER
G120X (230V,IP20,3kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC18-1UP0	CONVERTER
G120X (230V,IP20,4kW,UF,USS,IOP-2,3C3)	6SL3230-3YC20-0UB0	CONVERTER
G120X (230V,IP20,4kW,UF,PN,IOP-2,3C3)	6SL3230-3YC20-0UF0	CONVERTER
G120X (230V,IP20,4kW,UF,DP,IOP-2,3C3)	6SL3230-3YC20-0UP0	CONVERTER
G120X (230V,IP20,4kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC20-1UB0	CONVERTER

G120X (230V,IP20,4kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC20-1UF0	CONVERTER
G120X (230V,IP20,4kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC20-1UP0	CONVERTER
G120X (230V,IP20,5.5kW,UF,USS,IOP-2,3C3)	6SL3230-3YC22-0UB0	CONVERTER
G120X (230V,IP20,5.5kW,UF,PN,IOP-2,3C3)	6SL3230-3YC22-0UF0	CONVERTER
G120X (230V,IP20,5.5kW,UF,DP,IOP-2,3C3)	6SL3230-3YC22-0UP0	CONVERTER
G120X (230V,IP20,5.5kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC22-1UB0	CONVERTER
G120X (230V,IP20,5.5kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC22-1UF0	CONVERTER
G120X (230V,IP20,5.5kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC22-1UP0	CONVERTER
G120X (230V,IP20,7.5kW,UF,USS,IOP-2,3C3)	6SL3230-3YC24-0UB0	CONVERTER
G120X (230V,IP20,7.5kW,UF,PN,IOP-2,3C3)	6SL3230-3YC24-0UF0	CONVERTER
G120X (230V,IP20,7.5kW,UF,DP,IOP-2,3C3)	6SL3230-3YC24-0UP0	CONVERTER
G120X (230V,IP20,7.5kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC24-1UB0	CONVERTER
G120X (230V,IP20,7.5kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC24-1UF0	CONVERTER
G120X (230V,IP20,7.5kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC24-1UP0	CONVERTER
G120X (230V,IP20,11kW,UF,USS,IOP-2,3C3)	6SL3230-3YC26-0UB0	CONVERTER
G120X (230V,IP20,11kW,UF,PN,IOP-2,3C3)	6SL3230-3YC26-0UF0	CONVERTER
G120X (230V,IP20,11kW,UF,DP,IOP-2,3C3)	6SL3230-3YC26-0UP0	CONVERTER
G120X (230V,IP20,11kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC26-1UB0	CONVERTER
G120X (230V,IP20,11kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC26-1UF0	CONVERTER
G120X (230V,IP20,11kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC26-1UP0	CONVERTER
G120X (230V,IP20,15kW,UF,USS,IOP-2,3C3)	6SL3230-3YC28-0UB0	CONVERTER
G120X (230V,IP20,15kW,UF,PN,IOP-2,3C3)	6SL3230-3YC28-0UF0	CONVERTER
G120X (230V,IP20,15kW,UF,DP,IOP-2,3C3)	6SL3230-3YC28-0UP0	CONVERTER
G120X (230V,IP20,15kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC28-1UB0	CONVERTER
G120X (230V,IP20,15kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC28-1UF0	CONVERTER
G120X (230V,IP20,15kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC28-1UP0	CONVERTER
G120X (230V,IP20,18,5kW,UF,USS,IOP-2,3C3)	6SL3230-3YC30-0UB0	CONVERTER
G120X (230V,IP20,18,5kW,UF,PN,IOP-2,3C3)	6SL3230-3YC30-0UF0	CONVERTER
G120X (230V,IP20,18,5kW,UF,DP,IOP-2,3C3)	6SL3230-3YC30-0UP0	CONVERTER
G120X (230V,IP20,18,5kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC30-1UB0	CONVERTER
G120X (230V,IP20,18,5kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC30-1UF0	CONVERTER
G120X (230V,IP20,18,5kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC30-1UP0	CONVERTER
G120X (230V,IP20,22kW,UF,USS,IOP-2,3C3)	6SL3230-3YC32-0UB0	CONVERTER
G120X (230V,IP20,22kW,UF,PN,IOP-2,3C3)	6SL3230-3YC32-0UF0	CONVERTER
G120X (230V,IP20,22kW,UF,DP,IOP-2,3C3)	6SL3230-3YC32-0UP0	CONVERTER
G120X (230V,IP20,22kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC32-1UB0	CONVERTER
G120X (230V,IP20,22kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC32-1UF0	CONVERTER
G120X (230V,IP20,22kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC32-1UP0	CONVERTER
G120X (230V,IP20,30kW,UF,USS,IOP-2,3C3)	6SL3230-3YC34-0UB0	CONVERTER
G120X (230V,IP20,30kW,UF,PN,IOP-2,3C3)	6SL3230-3YC34-0UF0	CONVERTER
G120X (230V,IP20,30kW,UF,DP,IOP-2,3C3)	6SL3230-3YC34-0UP0	CONVERTER
G120X (230V,IP20,30kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC34-1UB0	CONVERTER
G120X (230V,IP20,30kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC34-1UF0	CONVERTER
G120X (230V,IP20,30kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC34-1UP0	CONVERTER

G120X (230V,IP20,37kW,UF,USS,IOP-2,3C3)	6SL3230-3YC36-0UB0	CONVERTER
G120X (230V,IP20,37kW,UF,PN,IOP-2,3C3)	6SL3230-3YC36-0UF0	CONVERTER
G120X (230V,IP20,37kW,UF,DP,IOP-2,3C3)	6SL3230-3YC36-0UP0	CONVERTER
G120X (230V,IP20,37kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC36-1UB0	CONVERTER
G120X (230V,IP20,37kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC36-1UF0	CONVERTER
G120X (230V,IP20,37kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC36-1UP0	CONVERTER
G120X (230V,IP20,45kW,UF,USS,IOP-2,3C3)	6SL3230-3YC38-0UB0	CONVERTER
G120X (230V,IP20,45kW,UF,PN,IOP-2,3C3)	6SL3230-3YC38-0UF0	CONVERTER
G120X (230V,IP20,45kW,UF,DP,IOP-2,3C3)	6SL3230-3YC38-0UP0	CONVERTER
G120X (230V,IP20,45kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC38-1UB0	CONVERTER
G120X (230V,IP20,45kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC38-1UF0	CONVERTER
G120X (230V,IP20,45kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC38-1UP0	CONVERTER
G120X (230V,IP20,55kW,UF,USS,IOP-2,3C3)	6SL3230-3YC40-0UB0	CONVERTER
G120X (230V,IP20,55kW,UF,PN,IOP-2,3C3)	6SL3230-3YC40-0UF0	CONVERTER
G120X (230V,IP20,55kW,UF,DP,IOP-2,3C3)	6SL3230-3YC40-0UP0	CONVERTER
G120X (230V,IP20,55kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YC40-1UB0	CONVERTER
G120X (230V,IP20,55kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YC40-1UF0	CONVERTER
G120X (230V,IP20,55kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YC40-1UP0	CONVERTER
G120X (400V,IP20,0.75kW,C2,USS,IOP-2,3C3)	6SL3230-3YE10-0AB0	CONVERTER
G120X (400V,IP20,0.75kW,C2,PN,IOP-2,3C3)	6SL3230-3YE10-0AF0	CONVERTER
G120X (400V,IP20,0.75kW,C2,DP,IOP-2,3C3)	6SL3230-3YE10-0AP0	CONVERTER
G120X (400V,IP20,0.75kW,UF,USS,IOP-2,3C3)	6SL3230-3YE10-0UB0	CONVERTER
G120X (400V,IP20,0.75kW,UF,PN,IOP-2,3C3)	6SL3230-3YE10-0UF0	CONVERTER
G120X (400V,IP20,0.75kW,UF,DP,IOP-2,3C3)	6SL3230-3YE10-0UP0	CONVERTER
G120X (400V,IP20,0.75kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE10-1AB0	CONVERTER
G120X (400V,IP20,0.75kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE10-1AF0	CONVERTER
G120X (400V,IP20,0.75kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE10-1AP0	CONVERTER
G120X (400V,IP20,0.75kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE10-1UB0	CONVERTER
G120X (400V,IP20,0.75kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE10-1UF0	CONVERTER
G120X (400V,IP20,0.75kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE10-1UP0	CONVERTER
G120X (400V,IP20,1.1kW,C2,USS,IOP-2,3C3)	6SL3230-3YE12-0AB0	CONVERTER
G120X (400V,IP20,1.1kW,C2,PN,IOP-2,3C3)	6SL3230-3YE12-0AF0	CONVERTER
G120X (400V,IP20,1.1kW,C2,DP,IOP-2,3C3)	6SL3230-3YE12-0AP0	CONVERTER
G120X (400V,IP20,1.1kW,UF,USS,IOP-2,3C3)	6SL3230-3YE12-0UB0	CONVERTER
G120X (400V,IP20,1.1kW,UF,PN,IOP-2,3C3)	6SL3230-3YE12-0UF0	CONVERTER
G120X (400V,IP20,1.1kW,UF,DP,IOP-2,3C3)	6SL3230-3YE12-0UP0	CONVERTER
G120X (400V,IP20,1.1kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE12-1AB0	CONVERTER
G120X (400V,IP20,1.1kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE12-1AF0	CONVERTER
G120X (400V,IP20,1.1kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE12-1AP0	CONVERTER
G120X (400V,IP20,1.1kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE12-1UB0	CONVERTER
G120X (400V,IP20,1.1kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE12-1UF0	CONVERTER
G120X (400V,IP20,1.1kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE12-1UP0	CONVERTER
G120X (400V,IP20,1.5kW,C2,USS,IOP-2,3C3)	6SL3230-3YE14-0AB0	CONVERTER
G120X (400V,IP20,1.5kW,C2,PN,IOP-2,3C3)	6SL3230-3YE14-0AF0	CONVERTER

G120X (400V,IP20,1.5kW,C2,DP,IOP-2,3C3)	6SL3230-3YE14-0AP0	CONVERTER
G120X (400V,IP20,1.5kW,UF,USS,IOP-2,3C3)	6SL3230-3YE14-0UB0	CONVERTER
G120X (400V,IP20,1.5kW,UF,PN,IOP-2,3C3)	6SL3230-3YE14-0UF0	CONVERTER
G120X (400V,IP20,1.5kW,UF,DP,IOP-2,3C3)	6SL3230-3YE14-0UP0	CONVERTER
G120X (400V,IP20,1.5kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE14-1AB0	CONVERTER
G120X (400V,IP20,1.5kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE14-1AF0	CONVERTER
G120X (400V,IP20,1.5kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE14-1AP0	CONVERTER
G120X (400V,IP20,1.5kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE14-1UB0	CONVERTER
G120X (400V,IP20,1.5kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE14-1UF0	CONVERTER
G120X (400V,IP20,1.5kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE14-1UP0	CONVERTER
G120X (400V,IP20,2.2kW,C2,USS,IOP-2,3C3)	6SL3230-3YE16-0AB0	CONVERTER
G120X (400V,IP20,2.2kW,C2,PN,IOP-2,3C3)	6SL3230-3YE16-0AF0	CONVERTER
G120X (400V,IP20,2.2kW,C2,DP,IOP-2,3C3)	6SL3230-3YE16-0AP0	CONVERTER
G120X (400V,IP20,2.2kW,UF,USS,IOP-2,3C3)	6SL3230-3YE16-0UB0	CONVERTER
G120X (400V,IP20,2.2kW,UF,PN,IOP-2,3C3)	6SL3230-3YE16-0UF0	CONVERTER
G120X (400V,IP20,2.2kW,UF,DP,IOP-2,3C3)	6SL3230-3YE16-0UP0	CONVERTER
G120X (400V,IP20,2.2kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE16-1AB0	CONVERTER
G120X (400V,IP20,2.2kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE16-1AF0	CONVERTER
G120X (400V,IP20,2.2kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE16-1AP0	CONVERTER
G120X (400V,IP20,2.2kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE16-1UB0	CONVERTER
G120X (400V,IP20,2.2kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE16-1UF0	CONVERTER
G120X (400V,IP20,2.2kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE16-1UP0	CONVERTER
G120X (400V,IP20,3kW,C2,USS,IOP-2,3C3)	6SL3230-3YE18-0AB0	CONVERTER
G120X (400V,IP20,3kW,C2,PN,IOP-2,3C3)	6SL3230-3YE18-0AF0	CONVERTER
G120X (400V,IP20,3kW,C2,DP,IOP-2,3C3)	6SL3230-3YE18-0AP0	CONVERTER
G120X (400V,IP20,3kW,UF,USS,IOP-2,3C3)	6SL3230-3YE18-0UB0	CONVERTER
G120X (400V,IP20,3kW,UF,PN,IOP-2,3C3)	6SL3230-3YE18-0UF0	CONVERTER
G120X (400V,IP20,3kW,UF,DP,IOP-2,3C3)	6SL3230-3YE18-0UP0	CONVERTER
G120X (400V,IP20,3kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE18-1AB0	CONVERTER
G120X (400V,IP20,3kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE18-1AF0	CONVERTER
G120X (400V,IP20,3kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE18-1AP0	CONVERTER
G120X (400V,IP20,3kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE18-1UB0	CONVERTER
G120X (400V,IP20,3kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE18-1UF0	CONVERTER
G120X (400V,IP20,3kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE18-1UP0	CONVERTER
G120X (400V,IP20,4kW,C2,USS,IOP-2,3C3)	6SL3230-3YE20-0AB0	CONVERTER
G120X (400V,IP20,4kW,C2,PN,IOP-2,3C3)	6SL3230-3YE20-0AF0	CONVERTER
G120X (400V,IP20,4kW,C2,DP,IOP-2,3C3)	6SL3230-3YE20-0AP0	CONVERTER
G120X (400V,IP20,4kW,UF,USS,IOP-2,3C3)	6SL3230-3YE20-0UB0	CONVERTER
G120X (400V,IP20,4kW,UF,PN,IOP-2,3C3)	6SL3230-3YE20-0UF0	CONVERTER
G120X (400V,IP20,4kW,UF,DP,IOP-2,3C3)	6SL3230-3YE20-0UP0	CONVERTER
G120X (400V,IP20,4kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE20-1AB0	CONVERTER
G120X (400V,IP20,4kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE20-1AF0	CONVERTER
G120X (400V,IP20,4kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE20-1AP0	CONVERTER
G120X (400V,IP20,4kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE20-1UB0	CONVERTER

G120X (400V,IP20,4kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE20-1UF0	CONVERTER
G120X (400V,IP20,4kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE20-1UP0	CONVERTER
G120X (400V,IP20,5.5kW,C2,USS,IOP-2,3C3)	6SL3230-3YE22-0AB0	CONVERTER
G120X (400V,IP20,5.5kW,C2,PN,IOP-2,3C3)	6SL3230-3YE22-0AF0	CONVERTER
G120X (400V,IP20,5.5kW,C2,DP,IOP-2,3C3)	6SL3230-3YE22-0AP0	CONVERTER
G120X (400V,IP20,5.5kW,UF,USS,IOP-2,3C3)	6SL3230-3YE22-0UB0	CONVERTER
G120X (400V,IP20,5.5kW,UF,PN,IOP-2,3C3)	6SL3230-3YE22-0UF0	CONVERTER
G120X (400V,IP20,5.5kW,UF,DP,IOP-2,3C3)	6SL3230-3YE22-0UP0	CONVERTER
G120X (400V,IP20,5.5kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE22-1AB0	CONVERTER
G120X (400V,IP20,5.5kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE22-1AF0	CONVERTER
G120X (400V,IP20,5.5kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE22-1AP0	CONVERTER
G120X (400V,IP20,5.5kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE22-1UB0	CONVERTER
G120X (400V,IP20,5.5kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE22-1UF0	CONVERTER
G120X (400V,IP20,5.5kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE22-1UP0	CONVERTER
G120X (400V,IP20,7.5kW,C2,USS,IOP-2,3C3)	6SL3230-3YE24-0AB0	CONVERTER
G120X (400V,IP20,7.5kW,C2,PN,IOP-2,3C3)	6SL3230-3YE24-0AF0	CONVERTER
G120X (400V,IP20,7.5kW,C2,DP,IOP-2,3C3)	6SL3230-3YE24-0AP0	CONVERTER
G120X (400V,IP20,7.5kW,UF,USS,IOP-2,3C3)	6SL3230-3YE24-0UB0	CONVERTER
G120X (400V,IP20,7.5kW,UF,PN,IOP-2,3C3)	6SL3230-3YE24-0UF0	CONVERTER
G120X (400V,IP20,7.5kW,UF,DP,IOP-2,3C3)	6SL3230-3YE24-0UP0	CONVERTER
G120X (400V,IP20,7.5kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE24-1AB0	CONVERTER
G120X (400V,IP20,7.5kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE24-1AF0	CONVERTER
G120X (400V,IP20,7.5kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE24-1AP0	CONVERTER
G120X (400V,IP20,7.5kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE24-1UB0	CONVERTER
G120X (400V,IP20,7.5kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE24-1UF0	CONVERTER
G120X (400V,IP20,7.5kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE24-1UP0	CONVERTER
G120X (400V,IP20,11kW,C2,USS,IOP-2,3C3)	6SL3230-3YE26-0AB0	CONVERTER
G120X (400V,IP20,11kW,C2,PN,IOP-2,3C3)	6SL3230-3YE26-0AF0	CONVERTER
G120X (400V,IP20,11kW,C2,DP,IOP-2,3C3)	6SL3230-3YE26-0AP0	CONVERTER
G120X (400V,IP20,11kW,UF,USS,IOP-2,3C3)	6SL3230-3YE26-0UB0	CONVERTER
G120X (400V,IP20,11kW,UF,PN,IOP-2,3C3)	6SL3230-3YE26-0UF0	CONVERTER
G120X (400V,IP20,11kW,UF,DP,IOP-2,3C3)	6SL3230-3YE26-0UP0	CONVERTER
G120X (400V,IP20,11kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE26-1AB0	CONVERTER
G120X (400V,IP20,11kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE26-1AF0	CONVERTER
G120X (400V,IP20,11kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE26-1AP0	CONVERTER
G120X (400V,IP20,11kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE26-1UB0	CONVERTER
G120X (400V,IP20,11kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE26-1UF0	CONVERTER
G120X (400V,IP20,11kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE26-1UP0	CONVERTER
G120X (400V,IP20,15kW,C2,USS,IOP-2,3C3)	6SL3230-3YE28-0AB0	CONVERTER
G120X (400V,IP20,15kW,C2,PN,IOP-2,3C3)	6SL3230-3YE28-0AF0	CONVERTER
G120X (400V,IP20,15kW,C2,DP,IOP-2,3C3)	6SL3230-3YE28-0AP0	CONVERTER
G120X (400V,IP20,15kW,UF,USS,IOP-2,3C3)	6SL3230-3YE28-0UB0	CONVERTER
G120X (400V,IP20,15kW,UF,PN,IOP-2,3C3)	6SL3230-3YE28-0UF0	CONVERTER
G120X (400V,IP20,15kW,UF,DP,IOP-2,3C3)	6SL3230-3YE28-0UP0	CONVERTER

G120X (400V,IP20,15kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE28-1AB0	CONVERTER
G120X (400V,IP20,15kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE28-1AF0	CONVERTER
G120X (400V,IP20,15kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE28-1AP0	CONVERTER
G120X (400V,IP20,15kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE28-1UB0	CONVERTER
G120X (400V,IP20,15kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE28-1UF0	CONVERTER
G120X (400V,IP20,15kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE28-1UP0	CONVERTER
G120X (400V,IP20,18,5kW,C2,USS,IOP-2,3C3)	6SL3230-3YE30-0AB0	CONVERTER
G120X (400V,IP20,18,5kW,C2,PN,IOP-2,3C3)	6SL3230-3YE30-0AF0	CONVERTER
G120X (400V,IP20,18,5kW,C2,DP,IOP-2,3C3)	6SL3230-3YE30-0AP0	CONVERTER
G120X (400V,IP20,18,5kW,UF,USS,IOP-2,3C3)	6SL3230-3YE30-0UB0	CONVERTER
G120X (400V,IP20,18,5kW,UF,PN,IOP-2,3C3)	6SL3230-3YE30-0UF0	CONVERTER
G120X (400V,IP20,18,5kW,UF,DP,IOP-2,3C3)	6SL3230-3YE30-0UP0	CONVERTER
G120X (400V,IP20,18,5kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE30-1AB0	CONVERTER
G120X (400V,IP20,18,5kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE30-1AF0	CONVERTER
G120X (400V,IP20,18,5kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE30-1AP0	CONVERTER
G120X (400V,IP20,18,5kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE30-1UB0	CONVERTER
G120X (400V,IP20,18,5kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE30-1UF0	CONVERTER
G120X (400V,IP20,18,5kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE30-1UP0	CONVERTER
G120X (400V,IP20,22kW,C2,USS,IOP-2,3C3)	6SL3230-3YE32-0AB0	CONVERTER
G120X (400V,IP20,22kW,C2,PN,IOP-2,3C3)	6SL3230-3YE32-0AF0	CONVERTER
G120X (400V,IP20,22kW,C2,DP,IOP-2,3C3)	6SL3230-3YE32-0AP0	CONVERTER
G120X (400V,IP20,22kW,UF,USS,IOP-2,3C3)	6SL3230-3YE32-0UB0	CONVERTER
G120X (400V,IP20,22kW,UF,PN,IOP-2,3C3)	6SL3230-3YE32-0UF0	CONVERTER
G120X (400V,IP20,22kW,UF,DP,IOP-2,3C3)	6SL3230-3YE32-0UP0	CONVERTER
G120X (400V,IP20,22kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE32-1AB0	CONVERTER
G120X (400V,IP20,22kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE32-1AF0	CONVERTER
G120X (400V,IP20,22kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE32-1AP0	CONVERTER
G120X (400V,IP20,22kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE32-1UB0	CONVERTER
G120X (400V,IP20,22kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE32-1UF0	CONVERTER
G120X (400V,IP20,22kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE32-1UP0	CONVERTER
G120X (400V,IP20,30kW,C2,USS,IOP-2,3C3)	6SL3230-3YE34-0AB0	CONVERTER
G120X (400V,IP20,30kW,C2,PN,IOP-2,3C3)	6SL3230-3YE34-0AF0	CONVERTER
G120X (400V,IP20,30kW,C2,DP,IOP-2,3C3)	6SL3230-3YE34-0AP0	CONVERTER
G120X (400V,IP20,30kW,UF,USS,IOP-2,3C3)	6SL3230-3YE34-0UB0	CONVERTER
G120X (400V,IP20,30kW,UF,PN,IOP-2,3C3)	6SL3230-3YE34-0UF0	CONVERTER
G120X (400V,IP20,30kW,UF,DP,IOP-2,3C3)	6SL3230-3YE34-0UP0	CONVERTER
G120X (400V,IP20,30kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE34-1AB0	CONVERTER
G120X (400V,IP20,30kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE34-1AF0	CONVERTER
G120X (400V,IP20,30kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE34-1AP0	CONVERTER
G120X (400V,IP20,30kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE34-1UB0	CONVERTER
G120X (400V,IP20,30kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE34-1UF0	CONVERTER
G120X (400V,IP20,30kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE34-1UP0	CONVERTER
G120X (400V,IP20,37kW,C2,USS,IOP-2,3C3)	6SL3230-3YE36-0AB0	CONVERTER
G120X (400V,IP20,37kW,C2,PN,IOP-2,3C3)	6SL3230-3YE36-0AF0	CONVERTER

G120X (400V,IP20,37kW,C2,DP,IOP-2,3C3)	6SL3230-3YE36-0AP0	CONVERTER
G120X (400V,IP20,37kW,UF,USS,IOP-2,3C3)	6SL3230-3YE36-0UB0	CONVERTER
G120X (400V,IP20,37kW,UF,PN,IOP-2,3C3)	6SL3230-3YE36-0UF0	CONVERTER
G120X (400V,IP20,37kW,UF,DP,IOP-2,3C3)	6SL3230-3YE36-0UP0	CONVERTER
G120X (400V,IP20,37kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE36-1AB0	CONVERTER
G120X (400V,IP20,37kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE36-1AF0	CONVERTER
G120X (400V,IP20,37kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE36-1AP0	CONVERTER
G120X (400V,IP20,37kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE36-1UB0	CONVERTER
G120X (400V,IP20,37kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE36-1UF0	CONVERTER
G120X (400V,IP20,37kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE36-1UP0	CONVERTER
G120X (400V,IP20,45kW,C2,USS,IOP-2,3C3)	6SL3230-3YE38-0AB0	CONVERTER
G120X (400V,IP20,45kW,C2,PN,IOP-2,3C3)	6SL3230-3YE38-0AF0	CONVERTER
G120X (400V,IP20,45kW,C2,DP,IOP-2,3C3)	6SL3230-3YE38-0AP0	CONVERTER
G120X (400V,IP20,45kW,UF,USS,IOP-2,3C3)	6SL3230-3YE38-0UB0	CONVERTER
G120X (400V,IP20,45kW,UF,PN,IOP-2,3C3)	6SL3230-3YE38-0UF0	CONVERTER
G120X (400V,IP20,45kW,UF,DP,IOP-2,3C3)	6SL3230-3YE38-0UP0	CONVERTER
G120X (400V,IP20,45kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE38-1AB0	CONVERTER
G120X (400V,IP20,45kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE38-1AF0	CONVERTER
G120X (400V,IP20,45kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE38-1AP0	CONVERTER
G120X (400V,IP20,45kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE38-1UB0	CONVERTER
G120X (400V,IP20,45kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE38-1UF0	CONVERTER
G120X (400V,IP20,45kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE38-1UP0	CONVERTER
G120X (400V,IP20,55kW,C2,USS,IOP-2,3C3)	6SL3230-3YE40-0AB0	CONVERTER
G120X (400V,IP20,55kW,C2,PN,IOP-2,3C3)	6SL3230-3YE40-0AF0	CONVERTER
G120X (400V,IP20,55kW,C2,DP,IOP-2,3C3)	6SL3230-3YE40-0AP0	CONVERTER
G120X (400V,IP20,55kW,UF,USS,IOP-2,3C3)	6SL3230-3YE40-0UB0	CONVERTER
G120X (400V,IP20,55kW,UF,PN,IOP-2,3C3)	6SL3230-3YE40-0UF0	CONVERTER
G120X (400V,IP20,55kW,UF,DP,IOP-2,3C3)	6SL3230-3YE40-0UP0	CONVERTER
G120X (400V,IP20,55kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE40-1AB0	CONVERTER
G120X (400V,IP20,55kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE40-1AF0	CONVERTER
G120X (400V,IP20,55kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE40-1AP0	CONVERTER
G120X (400V,IP20,55kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE40-1UB0	CONVERTER
G120X (400V,IP20,55kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE40-1UF0	CONVERTER
G120X (400V,IP20,55kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE40-1UP0	CONVERTER
G120X (400V,IP20,75kW,C2,USS,IOP-2,3C3)	6SL3230-3YE42-0AB0	CONVERTER
G120X (400V,IP20,75kW,C2,USS,IOP-2,3C3)	6SL3230-3YE42-0AB6	CONVERTER
G120X (400V,IP20,75kW,C2,PN,IOP-2,3C3)	6SL3230-3YE42-0AF0	CONVERTER
G120X (400V,IP20,75kW,C2,PN,IOP-2,3C3)	6SL3230-3YE42-0AF6	CONVERTER
G120X (400V,IP20,75kW,C2,DP,IOP-2,3C3)	6SL3230-3YE42-0AP0	CONVERTER
G120X (400V,IP20,75kW,C2,DP,IOP-2,3C3)	6SL3230-3YE42-0AP6	CONVERTER
G120X (400V,IP20,75kW,UF,USS,IOP-2,3C3)	6SL3230-3YE42-0UB0	CONVERTER
G120X (400V,IP20,75kW,UF,USS,IOP-2,3C3)	6SL3230-3YE42-0UB6	CONVERTER
G120X (400V,IP20,75kW,UF,PN,IOP-2,3C3)	6SL3230-3YE42-0UF0	CONVERTER
G120X (400V,IP20,75kW,UF,PN,IOP-2,3C3)	6SL3230-3YE42-0UF6	CONVERTER

G120X (400V,IP20,75kW,UF,DP,IOP-2,3C3)	6SL3230-3YE42-0UP0	CONVERTER
G120X (400V,IP20,75kW,UF,DP,IOP-2,3C3)	6SL3230-3YE42-0UP6	CONVERTER
G120X (400V,IP20,75kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE42-1AB0	CONVERTER
G120X (400V,IP20,75kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE42-1AB6	CONVERTER
G120X (400V,IP20,75kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE42-1AF0	CONVERTER
G120X (400V,IP20,75kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE42-1AF6	CONVERTER
G120X (400V,IP20,75kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE42-1AP0	CONVERTER
G120X (400V,IP20,75kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE42-1AP6	CONVERTER
G120X (400V,IP20,75kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE42-1UB0	CONVERTER
G120X (400V,IP20,75kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE42-1UB6	CONVERTER
G120X (400V,IP20,75kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE42-1UF0	CONVERTER
G120X (400V,IP20,75kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE42-1UF6	CONVERTER
G120X (400V,IP20,75kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE42-1UP0	CONVERTER
G120X (400V,IP20,75kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE42-1UP6	CONVERTER
G120X (400V,IP20,90kW,C2,USS,IOP-2,3C3)	6SL3230-3YE44-0AB0	CONVERTER
G120X (400V,IP20,90kW,C2,USS,IOP-2,3C3)	6SL3230-3YE44-0AB6	CONVERTER
G120X (400V,IP20,90kW,C2,PN,IOP-2,3C3)	6SL3230-3YE44-0AF0	CONVERTER
G120X (400V,IP20,90kW,C2,PN,IOP-2,3C3)	6SL3230-3YE44-0AF6	CONVERTER
G120X (400V,IP20,90kW,C2,DP,IOP-2,3C3)	6SL3230-3YE44-0AP0	CONVERTER
G120X (400V,IP20,90kW,C2,DP,IOP-2,3C3)	6SL3230-3YE44-0AP6	CONVERTER
G120X (400V,IP20,90kW,UF,USS,IOP-2,3C3)	6SL3230-3YE44-0UB0	CONVERTER
G120X (400V,IP20,90kW,UF,USS,IOP-2,3C3)	6SL3230-3YE44-0UB6	CONVERTER
G120X (400V,IP20,90kW,UF,PN,IOP-2,3C3)	6SL3230-3YE44-0UF0	CONVERTER
G120X (400V,IP20,90kW,UF,PN,IOP-2,3C3)	6SL3230-3YE44-0UF6	CONVERTER
G120X (400V,IP20,90kW,UF,DP,IOP-2,3C3)	6SL3230-3YE44-0UP0	CONVERTER
G120X (400V,IP20,90kW,UF,DP,IOP-2,3C3)	6SL3230-3YE44-0UP6	CONVERTER
G120X (400V,IP20,90kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE44-1AB0	CONVERTER
G120X (400V,IP20,90kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE44-1AB6	CONVERTER
G120X (400V,IP20,90kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE44-1AF0	CONVERTER
G120X (400V,IP20,90kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE44-1AF6	CONVERTER
G120X (400V,IP20,90kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE44-1AP0	CONVERTER
G120X (400V,IP20,90kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE44-1AP6	CONVERTER
G120X (400V,IP20,90kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE44-1UB0	CONVERTER
G120X (400V,IP20,90kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE44-1UB6	CONVERTER
G120X (400V,IP20,90kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE44-1UF0	CONVERTER
G120X (400V,IP20,90kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE44-1UF6	CONVERTER
G120X (400V,IP20,90kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE44-1UP0	CONVERTER
G120X (400V,IP20,90kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE44-1UP6	CONVERTER
G120X (400V,IP20,110kW,C2,USS,IOP-2,3C3)	6SL3230-3YE46-0AB0	CONVERTER
G120X (400V,IP20,110kW,C2,USS,IOP-2,3C3)	6SL3230-3YE46-0AB6	CONVERTER
G120X (400V,IP20,110kW,C2,PN,IOP-2,3C3)	6SL3230-3YE46-0AF0	CONVERTER
G120X (400V,IP20,110kW,C2,PN,IOP-2,3C3)	6SL3230-3YE46-0AF6	CONVERTER
G120X (400V,IP20,110kW,C2,DP,IOP-2,3C3)	6SL3230-3YE46-0AP0	CONVERTER
G120X (400V,IP20,110kW,C2,DP,IOP-2,3C3)	6SL3230-3YE46-0AP6	CONVERTER

G120X (400V,IP20,110kW,UF,USS,IOP-2,3C3)	6SL3230-3YE46-0UB0	CONVERTER
G120X (400V,IP20,110kW,UF,USS,IOP-2,3C3)	6SL3230-3YE46-0UB6	CONVERTER
G120X (400V,IP20,110kW,UF,PN,IOP-2,3C3)	6SL3230-3YE46-0UF0	CONVERTER
G120X (400V,IP20,110kW,UF,PN,IOP-2,3C3)	6SL3230-3YE46-0UF6	CONVERTER
G120X (400V,IP20,110kW,UF,DP,IOP-2,3C3)	6SL3230-3YE46-0UP0	CONVERTER
G120X (400V,IP20,110kW,UF,DP,IOP-2,3C3)	6SL3230-3YE46-0UP6	CONVERTER
G120X (400V,IP20,110kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE46-1AB0	CONVERTER
G120X (400V,IP20,110kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE46-1AB6	CONVERTER
G120X (400V,IP20,110kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE46-1AF0	CONVERTER
G120X (400V,IP20,110kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE46-1AF6	CONVERTER
G120X (400V,IP20,110kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE46-1AP0	CONVERTER
G120X (400V,IP20,110kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE46-1AP6	CONVERTER
G120X (400V,IP20,110kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE46-1UB0	CONVERTER
G120X (400V,IP20,110kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE46-1UB6	CONVERTER
G120X (400V,IP20,110kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE46-1UF0	CONVERTER
G120X (400V,IP20,110kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE46-1UF6	CONVERTER
G120X (400V,IP20,110kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE46-1UP0	CONVERTER
G120X (400V,IP20,110kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE46-1UP6	CONVERTER
G120X (400V,IP20,132kW,C2,USS,IOP-2,3C3)	6SL3230-3YE48-0AB0	CONVERTER
G120X (400V,IP20,132kW,C2,USS,IOP-2,3C3)	6SL3230-3YE48-0AB6	CONVERTER
G120X (400V,IP20,132kW,C2,PN,IOP-2,3C3)	6SL3230-3YE48-0AF0	CONVERTER
G120X (400V,IP20,132kW,C2,PN,IOP-2,3C3)	6SL3230-3YE48-0AF6	CONVERTER
G120X (400V,IP20,132kW,C2,DP,IOP-2,3C3)	6SL3230-3YE48-0AP0	CONVERTER
G120X (400V,IP20,132kW,C2,DP,IOP-2,3C3)	6SL3230-3YE48-0AP6	CONVERTER
G120X (400V,IP20,132kW,UF,USS,IOP-2,3C3)	6SL3230-3YE48-0UB0	CONVERTER
G120X (400V,IP20,132kW,UF,USS,IOP-2,3C3)	6SL3230-3YE48-0UB6	CONVERTER
G120X (400V,IP20,132kW,UF,PN,IOP-2,3C3)	6SL3230-3YE48-0UF0	CONVERTER
G120X (400V,IP20,132kW,UF,PN,IOP-2,3C3)	6SL3230-3YE48-0UF6	CONVERTER
G120X (400V,IP20,132kW,UF,DP,IOP-2,3C3)	6SL3230-3YE48-0UP0	CONVERTER
G120X (400V,IP20,132kW,UF,DP,IOP-2,3C3)	6SL3230-3YE48-0UP6	CONVERTER
G120X (400V,IP20,132kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE48-1AB0	CONVERTER
G120X (400V,IP20,132kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE48-1AB6	CONVERTER
G120X (400V,IP20,132kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE48-1AF0	CONVERTER
G120X (400V,IP20,132kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE48-1AF6	CONVERTER
G120X (400V,IP20,132kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE48-1AP0	CONVERTER
G120X (400V,IP20,132kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE48-1AP6	CONVERTER
G120X (400V,IP20,132kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE48-1UB0	CONVERTER
G120X (400V,IP20,132kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YE48-1UB6	CONVERTER
G120X (400V,IP20,132kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE48-1UF0	CONVERTER
G120X (400V,IP20,132kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YE48-1UF6	CONVERTER
G120X (400V,IP20,132kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE48-1UP0	CONVERTER
G120X (400V,IP20,132kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YE48-1UP6	CONVERTER
G120X (400V,IP20,160kW,C2,USS,IOP-2,3C3)	6SL3230-3YE50-0AB0	CONVERTER
G120X (400V,IP20,160kW,C2,USS,IOP-2,3C3)	6SL3230-3YE50-0AB6	CONVERTER

G120X (400V,IP20,160kW,C2,PN,IOP-2,3C3)	6SL3230-3YE50-0AF0	CONVERTER
G120X (400V,IP20,160kW,C2,PN,IOP-2,3C3)	6SL3230-3YE50-0AF6	CONVERTER
G120X (400V,IP20,160kW,C2,DP,IOP-2,3C3)	6SL3230-3YE50-0AP0	CONVERTER
G120X (400V,IP20,160kW,C2,DP,IOP-2,3C3)	6SL3230-3YE50-0AP6	CONVERTER
G120X (400V,IP20,160kW,C3,USS,IOP-2,3C3)	6SL3230-3YE50-0CB0	CONVERTER
G120X (400V,IP20,160kW,C3,USS,IOP-2,3C3)	6SL3230-3YE50-0CB6	CONVERTER
G120X (400V,IP20,160kW,C3,PN,IOP-2,3C3)	6SL3230-3YE50-0CF0	CONVERTER
G120X (400V,IP20,160kW,C3,PN,IOP-2,3C3)	6SL3230-3YE50-0CF6	CONVERTER
G120X (400V,IP20,160kW,C3,DP,IOP-2,3C3)	6SL3230-3YE50-0CP0	CONVERTER
G120X (400V,IP20,160kW,C3,DP,IOP-2,3C3)	6SL3230-3YE50-0CP6	CONVERTER
G120X (400V,IP20,160kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE50-1AB0	CONVERTER
G120X (400V,IP20,160kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE50-1AB6	CONVERTER
G120X (400V,IP20,160kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE50-1AF0	CONVERTER
G120X (400V,IP20,160kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE50-1AF6	CONVERTER
G120X (400V,IP20,160kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE50-1AP0	CONVERTER
G120X (400V,IP20,160kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE50-1AP6	CONVERTER
G120X (400V,IP20,160kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YE50-1CB0	CONVERTER
G120X (400V,IP20,160kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YE50-1CB6	CONVERTER
G120X (400V,IP20,160kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YE50-1CF0	CONVERTER
G120X (400V,IP20,160kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YE50-1CF6	CONVERTER
G120X (400V,IP20,160kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YE50-1CP0	CONVERTER
G120X (400V,IP20,160kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YE50-1CP6	CONVERTER
G120X (400V,IP20,200kW,C2,USS,IOP-2,3C3)	6SL3230-3YE52-0AB0	CONVERTER
G120X (400V,IP20,200kW,C2,USS,IOP-2,3C3)	6SL3230-3YE52-0AB6	CONVERTER
G120X (400V,IP20,200kW,C2,PN,IOP-2,3C3)	6SL3230-3YE52-0AF0	CONVERTER
G120X (400V,IP20,200kW,C2,PN,IOP-2,3C3)	6SL3230-3YE52-0AF6	CONVERTER
G120X (400V,IP20,200kW,C2,DP,IOP-2,3C3)	6SL3230-3YE52-0AP0	CONVERTER
G120X (400V,IP20,200kW,C2,DP,IOP-2,3C3)	6SL3230-3YE52-0AP6	CONVERTER
G120X (400V,IP20,200kW,C3,USS,IOP-2,3C3)	6SL3230-3YE52-0CB0	CONVERTER
G120X (400V,IP20,200kW,C3,USS,IOP-2,3C3)	6SL3230-3YE52-0CB6	CONVERTER
G120X (400V,IP20,200kW,C3,PN,IOP-2,3C3)	6SL3230-3YE52-0CF0	CONVERTER
G120X (400V,IP20,200kW,C3,PN,IOP-2,3C3)	6SL3230-3YE52-0CF6	CONVERTER
G120X (400V,IP20,200kW,C3,DP,IOP-2,3C3)	6SL3230-3YE52-0CP0	CONVERTER
G120X (400V,IP20,200kW,C3,DP,IOP-2,3C3)	6SL3230-3YE52-0CP6	CONVERTER
G120X (400V,IP20,200kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE52-1AB0	CONVERTER
G120X (400V,IP20,200kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE52-1AB6	CONVERTER
G120X (400V,IP20,200kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE52-1AF0	CONVERTER
G120X (400V,IP20,200kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE52-1AF6	CONVERTER
G120X (400V,IP20,200kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE52-1AP0	CONVERTER
G120X (400V,IP20,200kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE52-1AP6	CONVERTER
G120X (400V,IP20,200kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YE52-1CB0	CONVERTER
G120X (400V,IP20,200kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YE52-1CB6	CONVERTER
G120X (400V,IP20,200kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YE52-1CF0	CONVERTER
G120X (400V,IP20,200kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YE52-1CF6	CONVERTER

G120X (400V,IP20,200kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YE52-1CP0	CONVERTER
G120X (400V,IP20,200kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YE52-1CP6	CONVERTER
G120X (400V,IP20,250kW,C2,USS,IOP-2,3C3)	6SL3230-3YE54-0AB0	CONVERTER
G120X (400V,IP20,250kW,C2,USS,IOP-2,3C3)	6SL3230-3YE54-0AB6	CONVERTER
G120X (400V,IP20,250kW,C2,PN,IOP-2,3C3)	6SL3230-3YE54-0AF0	CONVERTER
G120X (400V,IP20,250kW,C2,PN,IOP-2,3C3)	6SL3230-3YE54-0AF6	CONVERTER
G120X (400V,IP20,250kW,C2,DP,IOP-2,3C3)	6SL3230-3YE54-0AP0	CONVERTER
G120X (400V,IP20,250kW,C2,DP,IOP-2,3C3)	6SL3230-3YE54-0AP6	CONVERTER
G120X (400V,IP20,250kW,C3,USS,IOP-2,3C3)	6SL3230-3YE54-0CB0	CONVERTER
G120X (400V,IP20,250kW,C3,USS,IOP-2,3C3)	6SL3230-3YE54-0CB6	CONVERTER
G120X (400V,IP20,250kW,C3,PN,IOP-2,3C3)	6SL3230-3YE54-0CF0	CONVERTER
G120X (400V,IP20,250kW,C3,PN,IOP-2,3C3)	6SL3230-3YE54-0CF6	CONVERTER
G120X (400V,IP20,250kW,C3,DP,IOP-2,3C3)	6SL3230-3YE54-0CP0	CONVERTER
G120X (400V,IP20,250kW,C3,DP,IOP-2,3C3)	6SL3230-3YE54-0CP6	CONVERTER
G120X (400V,IP20,250kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE54-1AB0	CONVERTER
G120X (400V,IP20,250kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YE54-1AB6	CONVERTER
G120X (400V,IP20,250kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE54-1AF0	CONVERTER
G120X (400V,IP20,250kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YE54-1AF6	CONVERTER
G120X (400V,IP20,250kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE54-1AP0	CONVERTER
G120X (400V,IP20,250kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YE54-1AP6	CONVERTER
G120X (400V,IP20,250kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YE54-1CB0	CONVERTER
G120X (400V,IP20,250kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YE54-1CB6	CONVERTER
G120X (400V,IP20,250kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YE54-1CF0	CONVERTER
G120X (400V,IP20,250kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YE54-1CF6	CONVERTER
G120X (400V,IP20,250kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YE54-1CP0	CONVERTER
G120X (400V,IP20,250kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YE54-1CP6	CONVERTER
G120X (690V,IP20,3kW,C2,USS,IOP-2,3C3)	6SL3230-3YH18-0AB0	CONVERTER
G120X (690V,IP20,3kW,C2,PN,IOP-2,3C3)	6SL3230-3YH18-0AF0	CONVERTER
G120X (690V,IP20,3kW,C2,DP,IOP-2,3C3)	6SL3230-3YH18-0AP0	CONVERTER
G120X (690V,IP20,3kW,UF,USS,IOP-2,3C3)	6SL3230-3YH18-0UB0	CONVERTER
G120X (690V,IP20,3kW,UF,PN,IOP-2,3C3)	6SL3230-3YH18-0UF0	CONVERTER
G120X (690V,IP20,3kW,UF,DP,IOP-2,3C3)	6SL3230-3YH18-0UP0	CONVERTER
G120X (690V,IP20,3kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YH18-1AB0	CONVERTER
G120X (690V,IP20,3kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YH18-1AF0	CONVERTER
G120X (690V,IP20,3kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YH18-1AP0	CONVERTER
G120X (690V,IP20,3kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH18-1UB0	CONVERTER
G120X (690V,IP20,3kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH18-1UF0	CONVERTER
G120X (690V,IP20,3kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH18-1UP0	CONVERTER
G120X (690V,IP20,4kW,C2,USS,IOP-2,3C3)	6SL3230-3YH20-0AB0	CONVERTER
G120X (690V,IP20,4kW,C2,PN,IOP-2,3C3)	6SL3230-3YH20-0AF0	CONVERTER
G120X (690V,IP20,4kW,C2,DP,IOP-2,3C3)	6SL3230-3YH20-0AP0	CONVERTER
G120X (690V,IP20,4kW,UF,USS,IOP-2,3C3)	6SL3230-3YH20-0UB0	CONVERTER
G120X (690V,IP20,4kW,UF,PN,IOP-2,3C3)	6SL3230-3YH20-0UF0	CONVERTER
G120X (690V,IP20,4kW,UF,DP,IOP-2,3C3)	6SL3230-3YH20-0UP0	CONVERTER

G120X (690V,IP20,4kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YH20-1AB0	CONVERTER
G120X (690V,IP20,4kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YH20-1AF0	CONVERTER
G120X (690V,IP20,4kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YH20-1AP0	CONVERTER
G120X (690V,IP20,4kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH20-1UB0	CONVERTER
G120X (690V,IP20,4kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH20-1UF0	CONVERTER
G120X (690V,IP20,4kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH20-1UP0	CONVERTER
G120X (690V,IP20,5.5kW,C2,USS,IOP-2,3C3)	6SL3230-3YH22-0AB0	CONVERTER
G120X (690V,IP20,5.5kW,C2,PN,IOP-2,3C3)	6SL3230-3YH22-0AF0	CONVERTER
G120X (690V,IP20,5.5kW,C2,DP,IOP-2,3C3)	6SL3230-3YH22-0AP0	CONVERTER
G120X (690V,IP20,5.5kW,UF,USS,IOP-2,3C3)	6SL3230-3YH22-0UB0	CONVERTER
G120X (690V,IP20,5.5kW,UF,PN,IOP-2,3C3)	6SL3230-3YH22-0UF0	CONVERTER
G120X (690V,IP20,5.5kW,UF,DP,IOP-2,3C3)	6SL3230-3YH22-0UP0	CONVERTER
G120X (690V,IP20,5.5kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YH22-1AB0	CONVERTER
G120X (690V,IP20,5.5kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YH22-1AF0	CONVERTER
G120X (690V,IP20,5.5kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YH22-1AP0	CONVERTER
G120X (690V,IP20,5.5kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH22-1UB0	CONVERTER
G120X (690V,IP20,5.5kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH22-1UF0	CONVERTER
G120X (690V,IP20,5.5kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH22-1UP0	CONVERTER
G120X (690V,IP20,7.5kW,C2,USS,IOP-2,3C3)	6SL3230-3YH24-0AB0	CONVERTER
G120X (690V,IP20,7.5kW,C2,PN,IOP-2,3C3)	6SL3230-3YH24-0AF0	CONVERTER
G120X (690V,IP20,7.5kW,C2,DP,IOP-2,3C3)	6SL3230-3YH24-0AP0	CONVERTER
G120X (690V,IP20,7.5kW,UF,USS,IOP-2,3C3)	6SL3230-3YH24-0UB0	CONVERTER
G120X (690V,IP20,7.5kW,UF,PN,IOP-2,3C3)	6SL3230-3YH24-0UF0	CONVERTER
G120X (690V,IP20,7.5kW,UF,DP,IOP-2,3C3)	6SL3230-3YH24-0UP0	CONVERTER
G120X (690V,IP20,7.5kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YH24-1AB0	CONVERTER
G120X (690V,IP20,7.5kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YH24-1AF0	CONVERTER
G120X (690V,IP20,7.5kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YH24-1AP0	CONVERTER
G120X (690V,IP20,7.5kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH24-1UB0	CONVERTER
G120X (690V,IP20,7.5kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH24-1UF0	CONVERTER
G120X (690V,IP20,7.5kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH24-1UP0	CONVERTER
G120X (690V,IP20,11kW,C2,USS,IOP-2,3C3)	6SL3230-3YH26-0AB0	CONVERTER
G120X (690V,IP20,11kW,C2,PN,IOP-2,3C3)	6SL3230-3YH26-0AF0	CONVERTER
G120X (690V,IP20,11kW,C2,DP,IOP-2,3C3)	6SL3230-3YH26-0AP0	CONVERTER
G120X (690V,IP20,11kW,UF,USS,IOP-2,3C3)	6SL3230-3YH26-0UB0	CONVERTER
G120X (690V,IP20,11kW,UF,PN,IOP-2,3C3)	6SL3230-3YH26-0UF0	CONVERTER
G120X (690V,IP20,11kW,UF,DP,IOP-2,3C3)	6SL3230-3YH26-0UP0	CONVERTER
G120X (690V,IP20,11kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YH26-1AB0	CONVERTER
G120X (690V,IP20,11kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YH26-1AF0	CONVERTER
G120X (690V,IP20,11kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YH26-1AP0	CONVERTER
G120X (690V,IP20,11kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH26-1UB0	CONVERTER
G120X (690V,IP20,11kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH26-1UF0	CONVERTER
G120X (690V,IP20,11kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH26-1UP0	CONVERTER
G120X (690V,IP20,15kW,C2,USS,IOP-2,3C3)	6SL3230-3YH28-0AB0	CONVERTER
G120X (690V,IP20,15kW,C2,PN,IOP-2,3C3)	6SL3230-3YH28-0AF0	CONVERTER

G120X (690V,IP20,15kW,C2,DP,IOP-2,3C3)	6SL3230-3YH28-0AP0	CONVERTER
G120X (690V,IP20,15kW,UF,USS,IOP-2,3C3)	6SL3230-3YH28-0UB0	CONVERTER
G120X (690V,IP20,15kW,UF,PN,IOP-2,3C3)	6SL3230-3YH28-0UF0	CONVERTER
G120X (690V,IP20,15kW,UF,DP,IOP-2,3C3)	6SL3230-3YH28-0UP0	CONVERTER
G120X (690V,IP20,15kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YH28-1AB0	CONVERTER
G120X (690V,IP20,15kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YH28-1AF0	CONVERTER
G120X (690V,IP20,15kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YH28-1AP0	CONVERTER
G120X (690V,IP20,15kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH28-1UB0	CONVERTER
G120X (690V,IP20,15kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH28-1UF0	CONVERTER
G120X (690V,IP20,15kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH28-1UP0	CONVERTER
G120X (690V,IP20,18,5kW,C2,USS,IOP-2,3C3)	6SL3230-3YH30-0AB0	CONVERTER
G120X (690V,IP20,18,5kW,C2,PN,IOP-2,3C3)	6SL3230-3YH30-0AF0	CONVERTER
G120X (690V,IP20,18,5kW,C2,DP,IOP-2,3C3)	6SL3230-3YH30-0AP0	CONVERTER
G120X (690V,IP20,18,5kW,UF,USS,IOP-2,3C3)	6SL3230-3YH30-0UB0	CONVERTER
G120X (690V,IP20,18,5kW,UF,PN,IOP-2,3C3)	6SL3230-3YH30-0UF0	CONVERTER
G120X (690V,IP20,18,5kW,UF,DP,IOP-2,3C3)	6SL3230-3YH30-0UP0	CONVERTER
G120X (690V,IP20,18,5kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YH30-1AB0	CONVERTER
G120X (690V,IP20,18,5kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YH30-1AF0	CONVERTER
G120X (690V,IP20,18,5kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YH30-1AP0	CONVERTER
G120X (690V,IP20,18,5kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH30-1UB0	CONVERTER
G120X (690V,IP20,18,5kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH30-1UF0	CONVERTER
G120X (690V,IP20,18,5kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH30-1UP0	CONVERTER
G120X (690V,IP20,22kW,C2,USS,IOP-2,3C3)	6SL3230-3YH32-0AB0	CONVERTER
G120X (690V,IP20,22kW,C2,PN,IOP-2,3C3)	6SL3230-3YH32-0AF0	CONVERTER
G120X (690V,IP20,22kW,C2,DP,IOP-2,3C3)	6SL3230-3YH32-0AP0	CONVERTER
G120X (690V,IP20,22kW,UF,USS,IOP-2,3C3)	6SL3230-3YH32-0UB0	CONVERTER
G120X (690V,IP20,22kW,UF,PN,IOP-2,3C3)	6SL3230-3YH32-0UF0	CONVERTER
G120X (690V,IP20,22kW,UF,DP,IOP-2,3C3)	6SL3230-3YH32-0UP0	CONVERTER
G120X (690V,IP20,22kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YH32-1AB0	CONVERTER
G120X (690V,IP20,22kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YH32-1AF0	CONVERTER
G120X (690V,IP20,22kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YH32-1AP0	CONVERTER
G120X (690V,IP20,22kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH32-1UB0	CONVERTER
G120X (690V,IP20,22kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH32-1UF0	CONVERTER
G120X (690V,IP20,22kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH32-1UP0	CONVERTER
G120X (690V,IP20,30kW,C2,USS,IOP-2,3C3)	6SL3230-3YH34-0AB0	CONVERTER
G120X (690V,IP20,30kW,C2,PN,IOP-2,3C3)	6SL3230-3YH34-0AF0	CONVERTER
G120X (690V,IP20,30kW,C2,DP,IOP-2,3C3)	6SL3230-3YH34-0AP0	CONVERTER
G120X (690V,IP20,30kW,UF,USS,IOP-2,3C3)	6SL3230-3YH34-0UB0	CONVERTER
G120X (690V,IP20,30kW,UF,PN,IOP-2,3C3)	6SL3230-3YH34-0UF0	CONVERTER
G120X (690V,IP20,30kW,UF,DP,IOP-2,3C3)	6SL3230-3YH34-0UP0	CONVERTER
G120X (690V,IP20,30kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YH34-1AB0	CONVERTER
G120X (690V,IP20,30kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YH34-1AF0	CONVERTER
G120X (690V,IP20,30kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YH34-1AP0	CONVERTER
G120X (690V,IP20,30kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH34-1UB0	CONVERTER

G120X (690V,IP20,30kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH34-1UF0	CONVERTER
G120X (690V,IP20,30kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH34-1UP0	CONVERTER
G120X (690V,IP20,37kW,C2,USS,IOP-2,3C3)	6SL3230-3YH36-0AB0	CONVERTER
G120X (690V,IP20,37kW,C2,PN,IOP-2,3C3)	6SL3230-3YH36-0AF0	CONVERTER
G120X (690V,IP20,37kW,C2,DP,IOP-2,3C3)	6SL3230-3YH36-0AP0	CONVERTER
G120X (690V,IP20,37kW,UF,USS,IOP-2,3C3)	6SL3230-3YH36-0UB0	CONVERTER
G120X (690V,IP20,37kW,UF,PN,IOP-2,3C3)	6SL3230-3YH36-0UF0	CONVERTER
G120X (690V,IP20,37kW,UF,DP,IOP-2,3C3)	6SL3230-3YH36-0UP0	CONVERTER
G120X (690V,IP20,37kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YH36-1AB0	CONVERTER
G120X (690V,IP20,37kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YH36-1AF0	CONVERTER
G120X (690V,IP20,37kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YH36-1AP0	CONVERTER
G120X (690V,IP20,37kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH36-1UB0	CONVERTER
G120X (690V,IP20,37kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH36-1UF0	CONVERTER
G120X (690V,IP20,37kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH36-1UP0	CONVERTER
G120X (690V,IP20,45kW,C2,USS,IOP-2,3C3)	6SL3230-3YH38-0AB0	CONVERTER
G120X (690V,IP20,45kW,C2,PN,IOP-2,3C3)	6SL3230-3YH38-0AF0	CONVERTER
G120X (690V,IP20,45kW,C2,DP,IOP-2,3C3)	6SL3230-3YH38-0AP0	CONVERTER
G120X (690V,IP20,45kW,UF,USS,IOP-2,3C3)	6SL3230-3YH38-0UB0	CONVERTER
G120X (690V,IP20,45kW,UF,PN,IOP-2,3C3)	6SL3230-3YH38-0UF0	CONVERTER
G120X (690V,IP20,45kW,UF,DP,IOP-2,3C3)	6SL3230-3YH38-0UP0	CONVERTER
G120X (690V,IP20,45kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YH38-1AB0	CONVERTER
G120X (690V,IP20,45kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YH38-1AF0	CONVERTER
G120X (690V,IP20,45kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YH38-1AP0	CONVERTER
G120X (690V,IP20,45kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH38-1UB0	CONVERTER
G120X (690V,IP20,45kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH38-1UF0	CONVERTER
G120X (690V,IP20,45kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH38-1UP0	CONVERTER
G120X (690V,IP20,55kW,C2,USS,IOP-2,3C3)	6SL3230-3YH40-0AB0	CONVERTER
G120X (690V,IP20,55kW,C2,PN,IOP-2,3C3)	6SL3230-3YH40-0AF0	CONVERTER
G120X (690V,IP20,55kW,C2,DP,IOP-2,3C3)	6SL3230-3YH40-0AP0	CONVERTER
G120X (690V,IP20,55kW,UF,USS,IOP-2,3C3)	6SL3230-3YH40-0UB0	CONVERTER
G120X (690V,IP20,55kW,UF,PN,IOP-2,3C3)	6SL3230-3YH40-0UF0	CONVERTER
G120X (690V,IP20,55kW,UF,DP,IOP-2,3C3)	6SL3230-3YH40-0UP0	CONVERTER
G120X (690V,IP20,55kW,C2,USS,IOP-2,3C3,IO)	6SL3230-3YH40-1AB0	CONVERTER
G120X (690V,IP20,55kW,C2,PN,IOP-2,3C3,IO)	6SL3230-3YH40-1AF0	CONVERTER
G120X (690V,IP20,55kW,C2,DP,IOP-2,3C3,IO)	6SL3230-3YH40-1AP0	CONVERTER
G120X (690V,IP20,55kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH40-1UB0	CONVERTER
G120X (690V,IP20,55kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH40-1UF0	CONVERTER
G120X (690V,IP20,55kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH40-1UP0	CONVERTER
G120X (690V,IP20,75kW,C3,USS,IOP-2,3C3)	6SL3230-3YH42-0CB0	CONVERTER
G120X (690V,IP20,75kW,C3,USS,IOP-2,3C3)	6SL3230-3YH42-0CB6	CONVERTER
G120X (690V,IP20,75kW,C3,PN,IOP-2,3C3)	6SL3230-3YH42-0CF0	CONVERTER
G120X (690V,IP20,75kW,C3,PN,IOP-2,3C3)	6SL3230-3YH42-0CF6	CONVERTER
G120X (690V,IP20,75kW,C3,DP,IOP-2,3C3)	6SL3230-3YH42-0CP0	CONVERTER
G120X (690V,IP20,75kW,C3,DP,IOP-2,3C3)	6SL3230-3YH42-0CP6	CONVERTER

G120X (690V,IP20,75kW,UF,USS,IOP-2,3C3)	6SL3230-3YH42-0UB0	CONVERTER
G120X (690V,IP20,75kW,UF,USS,IOP-2,3C3)	6SL3230-3YH42-0UB6	CONVERTER
G120X (690V,IP20,75kW,UF,PN,IOP-2,3C3)	6SL3230-3YH42-0UF0	CONVERTER
G120X (690V,IP20,75kW,UF,PN,IOP-2,3C3)	6SL3230-3YH42-0UF6	CONVERTER
G120X (690V,IP20,75kW,UF,DP,IOP-2,3C3)	6SL3230-3YH42-0UP0	CONVERTER
G120X (690V,IP20,75kW,UF,DP,IOP-2,3C3)	6SL3230-3YH42-0UP6	CONVERTER
G120X (690V,IP20,75kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YH42-1CB0	CONVERTER
G120X (690V,IP20,75kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YH42-1CB6	CONVERTER
G120X (690V,IP20,75kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YH42-1CF0	CONVERTER
G120X (690V,IP20,75kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YH42-1CF6	CONVERTER
G120X (690V,IP20,75kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YH42-1CP0	CONVERTER
G120X (690V,IP20,75kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YH42-1CP6	CONVERTER
G120X (690V,IP20,75kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH42-1UB0	CONVERTER
G120X (690V,IP20,75kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH42-1UB6	CONVERTER
G120X (690V,IP20,75kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH42-1UF0	CONVERTER
G120X (690V,IP20,75kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH42-1UF6	CONVERTER
G120X (690V,IP20,75kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH42-1UP0	CONVERTER
G120X (690V,IP20,75kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH42-1UP6	CONVERTER
G120X (690V,IP20,90kW,C3,USS,IOP-2,3C3)	6SL3230-3YH44-0CB0	CONVERTER
G120X (690V,IP20,90kW,C3,USS,IOP-2,3C3)	6SL3230-3YH44-0CB6	CONVERTER
G120X (690V,IP20,90kW,C3,PN,IOP-2,3C3)	6SL3230-3YH44-0CF0	CONVERTER
G120X (690V,IP20,90kW,C3,PN,IOP-2,3C3)	6SL3230-3YH44-0CF6	CONVERTER
G120X (690V,IP20,90kW,C3,DP,IOP-2,3C3)	6SL3230-3YH44-0CP0	CONVERTER
G120X (690V,IP20,90kW,C3,DP,IOP-2,3C3)	6SL3230-3YH44-0CP6	CONVERTER
G120X (690V,IP20,90kW,UF,USS,IOP-2,3C3)	6SL3230-3YH44-0UB0	CONVERTER
G120X (690V,IP20,90kW,UF,USS,IOP-2,3C3)	6SL3230-3YH44-0UB6	CONVERTER
G120X (690V,IP20,90kW,UF,PN,IOP-2,3C3)	6SL3230-3YH44-0UF0	CONVERTER
G120X (690V,IP20,90kW,UF,PN,IOP-2,3C3)	6SL3230-3YH44-0UF6	CONVERTER
G120X (690V,IP20,90kW,UF,DP,IOP-2,3C3)	6SL3230-3YH44-0UP0	CONVERTER
G120X (690V,IP20,90kW,UF,DP,IOP-2,3C3)	6SL3230-3YH44-0UP6	CONVERTER
G120X (690V,IP20,90kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YH44-1CB0	CONVERTER
G120X (690V,IP20,90kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YH44-1CB6	CONVERTER
G120X (690V,IP20,90kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YH44-1CF0	CONVERTER
G120X (690V,IP20,90kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YH44-1CF6	CONVERTER
G120X (690V,IP20,90kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YH44-1CP0	CONVERTER
G120X (690V,IP20,90kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YH44-1CP6	CONVERTER
G120X (690V,IP20,90kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH44-1UB0	CONVERTER
G120X (690V,IP20,90kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH44-1UB6	CONVERTER
G120X (690V,IP20,90kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH44-1UF0	CONVERTER
G120X (690V,IP20,90kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH44-1UF6	CONVERTER
G120X (690V,IP20,90kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH44-1UP0	CONVERTER
G120X (690V,IP20,90kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH44-1UP6	CONVERTER
G120X (690V,IP20,110kW,C3,USS,IOP-2,3C3)	6SL3230-3YH46-0CB0	CONVERTER
G120X (690V,IP20,110kW,C3,USS,IOP-2,3C3)	6SL3230-3YH46-0CB6	CONVERTER

G120X (690V,IP20,110kW,C3,PN,IOP-2,3C3)	6SL3230-3YH46-0CF0	CONVERTER
G120X (690V,IP20,110kW,C3,PN,IOP-2,3C3)	6SL3230-3YH46-0CF6	CONVERTER
G120X (690V,IP20,110kW,C3,DP,IOP-2,3C3)	6SL3230-3YH46-0CP0	CONVERTER
G120X (690V,IP20,110kW,C3,DP,IOP-2,3C3)	6SL3230-3YH46-0CP6	CONVERTER
G120X (690V,IP20,110kW,UF,USS,IOP-2,3C3)	6SL3230-3YH46-0UB0	CONVERTER
G120X (690V,IP20,110kW,UF,USS,IOP-2,3C3)	6SL3230-3YH46-0UB6	CONVERTER
G120X (690V,IP20,110kW,UF,PN,IOP-2,3C3)	6SL3230-3YH46-0UF0	CONVERTER
G120X (690V,IP20,110kW,UF,PN,IOP-2,3C3)	6SL3230-3YH46-0UF6	CONVERTER
G120X (690V,IP20,110kW,UF,DP,IOP-2,3C3)	6SL3230-3YH46-0UP0	CONVERTER
G120X (690V,IP20,110kW,UF,DP,IOP-2,3C3)	6SL3230-3YH46-0UP6	CONVERTER
G120X (690V,IP20,110kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YH46-1CB0	CONVERTER
G120X (690V,IP20,110kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YH46-1CB6	CONVERTER
G120X (690V,IP20,110kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YH46-1CF0	CONVERTER
G120X (690V,IP20,110kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YH46-1CF6	CONVERTER
G120X (690V,IP20,110kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YH46-1CP0	CONVERTER
G120X (690V,IP20,110kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YH46-1CP6	CONVERTER
G120X (690V,IP20,110kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH46-1UB0	CONVERTER
G120X (690V,IP20,110kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH46-1UB6	CONVERTER
G120X (690V,IP20,110kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH46-1UF0	CONVERTER
G120X (690V,IP20,110kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH46-1UF6	CONVERTER
G120X (690V,IP20,110kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH46-1UP0	CONVERTER
G120X (690V,IP20,110kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH46-1UP6	CONVERTER
G120X (690V,IP20,132kW,C3,USS,IOP-2,3C3)	6SL3230-3YH48-0CB0	CONVERTER
G120X (690V,IP20,132kW,C3,USS,IOP-2,3C3)	6SL3230-3YH48-0CB6	CONVERTER
G120X (690V,IP20,132kW,C3,PN,IOP-2,3C3)	6SL3230-3YH48-0CF0	CONVERTER
G120X (690V,IP20,132kW,C3,PN,IOP-2,3C3)	6SL3230-3YH48-0CF6	CONVERTER
G120X (690V,IP20,132kW,C3,DP,IOP-2,3C3)	6SL3230-3YH48-0CP0	CONVERTER
G120X (690V,IP20,132kW,C3,DP,IOP-2,3C3)	6SL3230-3YH48-0CP6	CONVERTER
G120X (690V,IP20,132kW,UF,USS,IOP-2,3C3)	6SL3230-3YH48-0UB0	CONVERTER
G120X (690V,IP20,132kW,UF,USS,IOP-2,3C3)	6SL3230-3YH48-0UB6	CONVERTER
G120X (690V,IP20,132kW,UF,PN,IOP-2,3C3)	6SL3230-3YH48-0UF0	CONVERTER
G120X (690V,IP20,132kW,UF,PN,IOP-2,3C3)	6SL3230-3YH48-0UF6	CONVERTER
G120X (690V,IP20,132kW,UF,DP,IOP-2,3C3)	6SL3230-3YH48-0UP0	CONVERTER
G120X (690V,IP20,132kW,UF,DP,IOP-2,3C3)	6SL3230-3YH48-0UP6	CONVERTER
G120X (690V,IP20,132kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YH48-1CB0	CONVERTER
G120X (690V,IP20,132kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YH48-1CB6	CONVERTER
G120X (690V,IP20,132kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YH48-1CF0	CONVERTER
G120X (690V,IP20,132kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YH48-1CF6	CONVERTER
G120X (690V,IP20,132kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YH48-1CP0	CONVERTER
G120X (690V,IP20,132kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YH48-1CP6	CONVERTER
G120X (690V,IP20,132kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH48-1UB0	CONVERTER
G120X (690V,IP20,132kW,UF,USS,IOP-2,3C3,IO)	6SL3230-3YH48-1UB6	CONVERTER
G120X (690V,IP20,132kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH48-1UF0	CONVERTER
G120X (690V,IP20,132kW,UF,PN,IOP-2,3C3,IO)	6SL3230-3YH48-1UF6	CONVERTER

G120X (690V,IP20,132kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH48-1UP0	CONVERTER
G120X (690V,IP20,132kW,UF,DP,IOP-2,3C3,IO)	6SL3230-3YH48-1UP6	CONVERTER
G120X (690V,IP20,160kW,C3,USS,IOP-2,3C3)	6SL3230-3YH50-0CB0	CONVERTER
G120X (690V,IP20,160kW,C3,USS,IOP-2,3C3)	6SL3230-3YH50-0CB6	CONVERTER
G120X (690V,IP20,160kW,C3,PN,IOP-2,3C3)	6SL3230-3YH50-0CF0	CONVERTER
G120X (690V,IP20,160kW,C3,PN,IOP-2,3C3)	6SL3230-3YH50-0CF6	CONVERTER
G120X (690V,IP20,160kW,C3,DP,IOP-2,3C3)	6SL3230-3YH50-0CP0	CONVERTER
G120X (690V,IP20,160kW,C3,DP,IOP-2,3C3)	6SL3230-3YH50-0CP6	CONVERTER
G120X (690V,IP20,160kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YH50-1CB0	CONVERTER
G120X (690V,IP20,160kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YH50-1CB6	CONVERTER
G120X (690V,IP20,160kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YH50-1CF0	CONVERTER
G120X (690V,IP20,160kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YH50-1CF6	CONVERTER
G120X (690V,IP20,160kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YH50-1CP0	CONVERTER
G120X (690V,IP20,160kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YH50-1CP6	CONVERTER
G120X (690V,IP20,200kW,C3,USS,IOP-2,3C3)	6SL3230-3YH52-0CB0	CONVERTER
G120X (690V,IP20,200kW,C3,USS,IOP-2,3C3)	6SL3230-3YH52-0CB6	CONVERTER
G120X (690V,IP20,200kW,C3,PN,IOP-2,3C3)	6SL3230-3YH52-0CF0	CONVERTER
G120X (690V,IP20,200kW,C3,PN,IOP-2,3C3)	6SL3230-3YH52-0CF6	CONVERTER
G120X (690V,IP20,200kW,C3,DP,IOP-2,3C3)	6SL3230-3YH52-0CP0	CONVERTER
G120X (690V,IP20,200kW,C3,DP,IOP-2,3C3)	6SL3230-3YH52-0CP6	CONVERTER
G120X (690V,IP20,200kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YH52-1CB0	CONVERTER
G120X (690V,IP20,200kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YH52-1CB6	CONVERTER
G120X (690V,IP20,200kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YH52-1CF0	CONVERTER
G120X (690V,IP20,200kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YH52-1CF6	CONVERTER
G120X (690V,IP20,200kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YH52-1CP0	CONVERTER
G120X (690V,IP20,200kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YH52-1CP6	CONVERTER
G120X (690V,IP20,250kW,C3,USS,IOP-2,3C3)	6SL3230-3YH54-0CB0	CONVERTER
G120X (690V,IP20,250kW,C3,USS,IOP-2,3C3)	6SL3230-3YH54-0CB6	CONVERTER
G120X (690V,IP20,250kW,C3,PN,IOP-2,3C3)	6SL3230-3YH54-0CF0	CONVERTER
G120X (690V,IP20,250kW,C3,PN,IOP-2,3C3)	6SL3230-3YH54-0CF6	CONVERTER
G120X (690V,IP20,250kW,C3,DP,IOP-2,3C3)	6SL3230-3YH54-0CP0	CONVERTER
G120X (690V,IP20,250kW,C3,DP,IOP-2,3C3)	6SL3230-3YH54-0CP6	CONVERTER
G120X (690V,IP20,250kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YH54-1CB0	CONVERTER
G120X (690V,IP20,250kW,C3,USS,IOP-2,3C3,IO)	6SL3230-3YH54-1CB6	CONVERTER
G120X (690V,IP20,250kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YH54-1CF0	CONVERTER
G120X (690V,IP20,250kW,C3,PN,IOP-2,3C3,IO)	6SL3230-3YH54-1CF6	CONVERTER
G120X (690V,IP20,250kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YH54-1CP0	CONVERTER
G120X (690V,IP20,250kW,C3,DP,IOP-2,3C3,IO)	6SL3230-3YH54-1CP6	CONVERTER
G120XA		
G120XA (440V,IP20,0.75kW,C3,USS,Blanc,3C2)	6SL3220-1YD10-0CB0	CONVERTER
G120XA (440V,IP20,0.75kW,UF,USS,Blanc,3C2)	6SL3220-1YD10-0UB0	CONVERTER
G120XA (440V,IP20,1.1kW,C3,USS,Blanc,3C2)	6SL3220-1YD12-0CB0	CONVERTER
G120XA (440V,IP20,1.1kW,UF,USS,Blanc,3C2)	6SL3220-1YD12-0UB0	CONVERTER
G120XA (440V,IP20,1.5kW,C3,USS,Blanc,3C2)	6SL3220-1YD14-0CB0	CONVERTER

G120XA (440V,IP20,1.5kW,UF,USS,Blanc,3C2)	6SL3220-1YD14-0UB0	CONVERTER
G120XA (440V,IP20,2.2kW,C3,USS,Blanc,3C2)	6SL3220-1YD16-0CB0	CONVERTER
G120XA (440V,IP20,2.2kW,UF,USS,Blanc,3C2)	6SL3220-1YD16-0UB0	CONVERTER
G120XA (440V,IP20,3kW,C3,USS,Blanc,3C2)	6SL3220-1YD18-0CB0	CONVERTER
G120XA (440V,IP20,3kW,UF,USS,Blanc,3C2)	6SL3220-1YD18-0UB0	CONVERTER
G120XA (440V,IP20,4kW,C3,USS,Blanc,3C2)	6SL3220-1YD20-0CB0	CONVERTER
G120XA (440V,IP20,4kW,UF,USS,Blanc,3C2)	6SL3220-1YD20-0UB0	CONVERTER
G120XA (440V,IP20,5.5kW,C3,USS,Blanc,3C2)	6SL3220-1YD22-0CB0	CONVERTER
G120XA (440V,IP20,5.5kW,UF,USS,Blanc,3C2)	6SL3220-1YD22-0UB0	CONVERTER
G120XA (440V,IP20,7.5kW,C3,USS,Blanc,3C2)	6SL3220-1YD24-0CB0	CONVERTER
G120XA (440V,IP20,7.5kW,UF,USS,Blanc,3C2)	6SL3220-1YD24-0UB0	CONVERTER
G120XA (440V,IP20,11kW,C3,USS,Blanc,3C2)	6SL3220-1YD26-0CB0	CONVERTER
G120XA (440V,IP20,11kW,UF,USS,Blanc,3C2)	6SL3220-1YD26-0UB0	CONVERTER
G120XA (440V,IP20,15kW,C3,USS,Blanc,3C2)	6SL3220-1YD28-0CB0	CONVERTER
G120XA (440V,IP20,15kW,UF,USS,Blanc,3C2)	6SL3220-1YD28-0UB0	CONVERTER
G120XA (440V,IP20,18,5kW,C3,USS,Blanc,3C2)	6SL3220-1YD30-0CB0	CONVERTER
G120XA (440V,IP20,18,5kW,UF,USS,Blanc,3C2)	6SL3220-1YD30-0UB0	CONVERTER
G120XA (440V,IP20,22kW,C3,USS,Blanc,3C2)	6SL3220-1YD32-0CB0	CONVERTER
G120XA (440V,IP20,22kW,UF,USS,Blanc,3C2)	6SL3220-1YD32-0UB0	CONVERTER
G120XA (440V,IP20,30kW,C3,USS,Blanc,3C2)	6SL3220-1YD34-0CB0	CONVERTER
G120XA (440V,IP20,30kW,UF,USS,Blanc,3C2)	6SL3220-1YD34-0UB0	CONVERTER
G120XA (440V,IP20,37kW,C3,USS,Blanc,3C2)	6SL3220-1YD36-0CB0	CONVERTER
G120XA (440V,IP20,37kW,UF,USS,Blanc,3C2)	6SL3220-1YD36-0UB0	CONVERTER
G120XA (440V,IP20,45kW,C3,USS,Blanc,3C2)	6SL3220-1YD38-0CB0	CONVERTER
G120XA (440V,IP20,45kW,UF,USS,Blanc,3C2)	6SL3220-1YD38-0UB0	CONVERTER
G120XA (440V,IP20,55kW,C3,USS,Blanc,3C2)	6SL3220-1YD40-0CB0	CONVERTER
G120XA (440V,IP20,55kW,UF,USS,Blanc,3C2)	6SL3220-1YD40-0UB0	CONVERTER
G120XA (440V,IP20,75kW,C3,USS,Blanc,3C2)	6SL3220-1YD42-0CB0	CONVERTER
G120XA (440V,IP20,75kW,UF,USS,Blanc,3C2)	6SL3220-1YD42-0UB0	CONVERTER
G120XA (440V,IP20,90kW,C3,USS,Blanc,3C2)	6SL3220-1YD44-0CB0	CONVERTER
G120XA (440V,IP20,90kW,UF,USS,Blanc,3C2)	6SL3220-1YD44-0UB0	CONVERTER
G120XA (440V,IP20,110kW,C3,USS,Blanc,3C2)	6SL3220-1YD46-0CB0	CONVERTER
G120XA (440V,IP20,110kW,UF,USS,Blanc,3C2)	6SL3220-1YD46-0UB0	CONVERTER
G120XA (440V,IP20,132kW,C3,USS,Blanc,3C2)	6SL3220-1YD48-0CB0	CONVERTER
G120XA (440V,IP20,132kW,UF,USS,Blanc,3C2)	6SL3220-1YD48-0UB0	CONVERTER
G120XA (440V,IP20,160kW,C3,USS,Blanc,3C2)	6SL3220-1YD50-0CB0	CONVERTER
G120XA (440V,IP20,200kW,C3,USS,Blanc,3C2)	6SL3220-1YD52-0CB0	CONVERTER
G120XA (440V,IP20,250kW,C3,USS,Blanc,3C2)	6SL3220-1YD54-0CB0	CONVERTER
G120XA (440V,IP20,315kW,C3,USS,Blanc,3C2)	6SL3220-1YD56-0CB0	CONVERTER
G120XA (440V,IP20,355kW,C3,USS,Blanc,3C2)	6SL3220-1YD58-0CB0	CONVERTER
G120XA (440V,IP20,400kW,C3,USS,Blanc,3C2)	6SL3220-1YD60-0CB0	CONVERTER
G120XA (440V,IP20,0.75kW,C3,USS,BOP-2,3C2)	6SL3220-2YD10-0CB0	CONVERTER
G120XA (440V,IP20,0.75kW,UF,USS,BOP-2,3C2)	6SL3220-2YD10-0UB0	CONVERTER
G120XA (440V,IP20,1.1kW,C3,USS,BOP-2,3C2)	6SL3220-2YD12-0CB0	CONVERTER

G120XA (440V,IP20,1.1kW,UF,USS,BOP-2,3C2)	6SL3220-2YD12-0UB0	CONVERTER
G120XA (440V,IP20,1.5kW,C3,USS,BOP-2,3C2)	6SL3220-2YD14-0CB0	CONVERTER
G120XA (440V,IP20,1.5kW,UF,USS,BOP-2,3C2)	6SL3220-2YD14-0UB0	CONVERTER
G120XA (440V,IP20,2.2kW,C3,USS,BOP-2,3C2)	6SL3220-2YD16-0CB0	CONVERTER
G120XA (440V,IP20,2.2kW,UF,USS,BOP-2,3C2)	6SL3220-2YD16-0UB0	CONVERTER
G120XA (440V,IP20,3kW,C3,USS,BOP-2,3C2)	6SL3220-2YD18-0CB0	CONVERTER
G120XA (440V,IP20,3kW,UF,USS,BOP-2,3C2)	6SL3220-2YD18-0UB0	CONVERTER
G120XA (440V,IP20,4kW,C3,USS,BOP-2,3C2)	6SL3220-2YD20-0CB0	CONVERTER
G120XA (440V,IP20,4kW,UF,USS,BOP-2,3C2)	6SL3220-2YD20-0UB0	CONVERTER
G120XA (440V,IP20,5.5kW,C3,USS,BOP-2,3C2)	6SL3220-2YD22-0CB0	CONVERTER
G120XA (440V,IP20,5.5kW,UF,USS,BOP-2,3C2)	6SL3220-2YD22-0UB0	CONVERTER
G120XA (440V,IP20,7.5kW,C3,USS,BOP-2,3C2)	6SL3220-2YD24-0CB0	CONVERTER
G120XA (440V,IP20,7.5kW,UF,USS,BOP-2,3C2)	6SL3220-2YD24-0UB0	CONVERTER
G120XA (440V,IP20,11kW,C3,USS,BOP-2,3C2)	6SL3220-2YD26-0CB0	CONVERTER
G120XA (440V,IP20,11kW,UF,USS,BOP-2,3C2)	6SL3220-2YD26-0UB0	CONVERTER
G120XA (440V,IP20,15kW,C3,USS,BOP-2,3C2)	6SL3220-2YD28-0CB0	CONVERTER
G120XA (440V,IP20,15kW,UF,USS,BOP-2,3C2)	6SL3220-2YD28-0UB0	CONVERTER
G120XA (440V,IP20,18,5kW,C3,USS,BOP-2,3C2)	6SL3220-2YD30-0CB0	CONVERTER
G120XA (440V,IP20,18,5kW,UF,USS,BOP-2,3C2)	6SL3220-2YD30-0UB0	CONVERTER
G120XA (440V,IP20,22kW,C3,USS,BOP-2,3C2)	6SL3220-2YD32-0CB0	CONVERTER
G120XA (440V,IP20,22kW,UF,USS,BOP-2,3C2)	6SL3220-2YD32-0UB0	CONVERTER
G120XA (440V,IP20,30kW,C3,USS,BOP-2,3C2)	6SL3220-2YD34-0CB0	CONVERTER
G120XA (440V,IP20,30kW,UF,USS,BOP-2,3C2)	6SL3220-2YD34-0UB0	CONVERTER
G120XA (440V,IP20,37kW,C3,USS,BOP-2,3C2)	6SL3220-2YD36-0CB0	CONVERTER
G120XA (440V,IP20,37kW,UF,USS,BOP-2,3C2)	6SL3220-2YD36-0UB0	CONVERTER
G120XA (440V,IP20,45kW,C3,USS,BOP-2,3C2)	6SL3220-2YD38-0CB0	CONVERTER
G120XA (440V,IP20,45kW,UF,USS,BOP-2,3C2)	6SL3220-2YD38-0UB0	CONVERTER
G120XA (440V,IP20,55kW,C3,USS,BOP-2,3C2)	6SL3220-2YD40-0CB0	CONVERTER
G120XA (440V,IP20,55kW,UF,USS,BOP-2,3C2)	6SL3220-2YD40-0UB0	CONVERTER
G120XA (440V,IP20,75kW,C3,USS,BOP-2,3C2)	6SL3220-2YD42-0CB0	CONVERTER
G120XA (440V,IP20,75kW,UF,USS,BOP-2,3C2)	6SL3220-2YD42-0UB0	CONVERTER
G120XA (440V,IP20,90kW,C3,USS,BOP-2,3C2)	6SL3220-2YD44-0CB0	CONVERTER
G120XA (440V,IP20,90kW,UF,USS,BOP-2,3C2)	6SL3220-2YD44-0UB0	CONVERTER
G120XA (440V,IP20,110kW,C3,USS,BOP-2,3C2)	6SL3220-2YD46-0CB0	CONVERTER
G120XA (440V,IP20,110kW,UF,USS,BOP-2,3C2)	6SL3220-2YD46-0UB0	CONVERTER
G120XA (440V,IP20,132kW,C3,USS,BOP-2,3C2)	6SL3220-2YD48-0CB0	CONVERTER
G120XA (440V,IP20,132kW,UF,USS,BOP-2,3C2)	6SL3220-2YD48-0UB0	CONVERTER
G120XA (440V,IP20,160kW,C3,USS,BOP-2,3C2)	6SL3220-2YD50-0CB0	CONVERTER
G120XA (440V,IP20,200kW,C3,USS,BOP-2,3C2)	6SL3220-2YD52-0CB0	CONVERTER
G120XA (440V,IP20,250kW,C3,USS,BOP-2,3C2)	6SL3220-2YD54-0CB0	CONVERTER
G120XA (440V,IP20,315kW,C3,USS,BOP-2,3C2)	6SL3220-2YD56-0CB0	CONVERTER
G120XA (440V,IP20,355kW,C3,USS,BOP-2,3C2)	6SL3220-2YD58-0CB0	CONVERTER
G120XA (440V,IP20,400kW,C3,USS,BOP-2,3C2)	6SL3220-2YD60-0CB0	CONVERTER
G120XA (440V,IP20,0.75kW,C3,USS,IOP-2,3C2)	6SL3220-3YD10-0CB0	CONVERTER

G120XA (440V,IP20,0.75kW,UF,USS,IOP-2,3C2)	6SL3220-3YD10-0UB0	CONVERTER
G120XA (440V,IP20,1.1kW,C3,USS,IOP-2,3C2)	6SL3220-3YD12-0CB0	CONVERTER
G120XA (440V,IP20,1.1kW,UF,USS,IOP-2,3C2)	6SL3220-3YD12-0UB0	CONVERTER
G120XA (440V,IP20,1.5kW,C3,USS,IOP-2,3C2)	6SL3220-3YD14-0CB0	CONVERTER
G120XA (440V,IP20,1.5kW,UF,USS,IOP-2,3C2)	6SL3220-3YD14-0UB0	CONVERTER
G120XA (440V,IP20,2.2kW,C3,USS,IOP-2,3C2)	6SL3220-3YD16-0CB0	CONVERTER
G120XA (440V,IP20,2.2kW,UF,USS,IOP-2,3C2)	6SL3220-3YD16-0UB0	CONVERTER
G120XA (440V,IP20,3kW,C3,USS,IOP-2,3C2)	6SL3220-3YD18-0CB0	CONVERTER
G120XA (440V,IP20,3kW,UF,USS,IOP-2,3C2)	6SL3220-3YD18-0UB0	CONVERTER
G120XA (440V,IP20,4kW,C3,USS,IOP-2,3C2)	6SL3220-3YD20-0CB0	CONVERTER
G120XA (440V,IP20,4kW,UF,USS,IOP-2,3C2)	6SL3220-3YD20-0UB0	CONVERTER
G120XA (440V,IP20,5.5kW,C3,USS,IOP-2,3C2)	6SL3220-3YD22-0CB0	CONVERTER
G120XA (440V,IP20,5.5kW,UF,USS,IOP-2,3C2)	6SL3220-3YD22-0UB0	CONVERTER
G120XA (440V,IP20,7.5kW,C3,USS,IOP-2,3C2)	6SL3220-3YD24-0CB0	CONVERTER
G120XA (440V,IP20,7.5kW,UF,USS,IOP-2,3C2)	6SL3220-3YD24-0UB0	CONVERTER
G120XA (440V,IP20,11kW,C3,USS,IOP-2,3C2)	6SL3220-3YD26-0CB0	CONVERTER
G120XA (440V,IP20,11kW,UF,USS,IOP-2,3C2)	6SL3220-3YD26-0UB0	CONVERTER
G120XA (440V,IP20,15kW,C3,USS,IOP-2,3C2)	6SL3220-3YD28-0CB0	CONVERTER
G120XA (440V,IP20,15kW,UF,USS,IOP-2,3C2)	6SL3220-3YD28-0UB0	CONVERTER
G120XA (440V,IP20,18,5kW,C3,USS,IOP-2,3C2)	6SL3220-3YD30-0CB0	CONVERTER
G120XA (440V,IP20,18,5kW,UF,USS,IOP-2,3C2)	6SL3220-3YD30-0UB0	CONVERTER
G120XA (440V,IP20,22kW,C3,USS,IOP-2,3C2)	6SL3220-3YD32-0CB0	CONVERTER
G120XA (440V,IP20,22kW,UF,USS,IOP-2,3C2)	6SL3220-3YD32-0UB0	CONVERTER
G120XA (440V,IP20,30kW,C3,USS,IOP-2,3C2)	6SL3220-3YD34-0CB0	CONVERTER
G120XA (440V,IP20,30kW,UF,USS,IOP-2,3C2)	6SL3220-3YD34-0UB0	CONVERTER
G120XA (440V,IP20,37kW,C3,USS,IOP-2,3C2)	6SL3220-3YD36-0CB0	CONVERTER
G120XA (440V,IP20,37kW,UF,USS,IOP-2,3C2)	6SL3220-3YD36-0UB0	CONVERTER
G120XA (440V,IP20,45kW,C3,USS,IOP-2,3C2)	6SL3220-3YD38-0CB0	CONVERTER
G120XA (440V,IP20,45kW,UF,USS,IOP-2,3C2)	6SL3220-3YD38-0UB0	CONVERTER
G120XA (440V,IP20,55kW,C3,USS,IOP-2,3C2)	6SL3220-3YD40-0CB0	CONVERTER
G120XA (440V,IP20,55kW,UF,USS,IOP-2,3C2)	6SL3220-3YD40-0UB0	CONVERTER
G120XA (440V,IP20,75kW,C3,USS,IOP-2,3C2)	6SL3220-3YD42-0CB0	CONVERTER
G120XA (440V,IP20,75kW,UF,USS,IOP-2,3C2)	6SL3220-3YD42-0UB0	CONVERTER
G120XA (440V,IP20,90kW,C3,USS,IOP-2,3C2)	6SL3220-3YD44-0CB0	CONVERTER
G120XA (440V,IP20,90kW,UF,USS,IOP-2,3C2)	6SL3220-3YD44-0UB0	CONVERTER
G120XA (440V,IP20,110kW,C3,USS,IOP-2,3C2)	6SL3220-3YD46-0CB0	CONVERTER
G120XA (440V,IP20,110kW,UF,USS,IOP-2,3C2)	6SL3220-3YD46-0UB0	CONVERTER
G120XA (440V,IP20,132kW,C3,USS,IOP-2,3C2)	6SL3220-3YD48-0CB0	CONVERTER
G120XA (440V,IP20,132kW,UF,USS,IOP-2,3C2)	6SL3220-3YD48-0UB0	CONVERTER
G120XA (440V,IP20,160kW,C3,USS,IOP-2,3C2)	6SL3220-3YD50-0CB0	CONVERTER
G120XA (440V,IP20,200kW,C3,USS,IOP-2,3C2)	6SL3220-3YD52-0CB0	CONVERTER
G120XA (440V,IP20,250kW,C3,USS,IOP-2,3C2)	6SL3220-3YD54-0CB0	CONVERTER
G120XA (440V,IP20,315kW,C3,USS,IOP-2,3C2)	6SL3220-3YD56-0CB0	CONVERTER
G120XA (440V,IP20,355kW,C3,USS,IOP-2,3C2)	6SL3220-3YD58-0CB0	CONVERTER

G120XA (440V,IP20,400kW,C3,USS,IOP-2,3C2)	6SL3220-3YD60-0CB0	CONVERTER
G120XA (440V,IP00,450kW,C3,USS,Blanc,3C2)	6SL3225-1YD62-0CB0	CONVERTER
G120XA (440V,IP00,500kW,C3,USS,Blanc,3C2)	6SL3225-1YD64-0CB0	CONVERTER
G120XA (440V,IP00,560kW,C3,USS,Blanc,3C2)	6SL3225-1YD66-0CB0	CONVERTER
G120XA (440V,IP00,450kW,C3,USS,BOP-2,3C2)	6SL3225-2YD62-0CB0	CONVERTER
G120XA (440V,IP00,500kW,C3,USS,BOP-2,3C2)	6SL3225-2YD64-0CB0	CONVERTER
G120XA (440V,IP00,560kW,C3,USS,BOP-2,3C2)	6SL3225-2YD66-0CB0	CONVERTER
G120XA (440V,IP00,450kW,C3,USS,IOP-2,3C2)	6SL3225-3YD62-0CB0	CONVERTER
G120XA (440V,IP00,500kW,C3,USS,IOP-2,3C2)	6SL3225-3YD64-0CB0	CONVERTER
G120XA (440V,IP00,560kW,C3,USS,IOP-2,3C2)	6SL3225-3YD66-0CB0	CONVERTER
G120XA (440V,IP20,0.75kW,C3,PN,Blanc,3C2)	6SL3220-1YD10-0CF0	CONVERTER
G120XA (440V,IP20,0.75kW,UF,PN,Blanc,3C2)	6SL3220-1YD10-0UF0	CONVERTER
G120XA (440V,IP20,1.1kW,C3,PN,Blanc,3C2)	6SL3220-1YD12-0CF0	CONVERTER
G120XA (440V,IP20,1.1kW,UF,PN,Blanc,3C2)	6SL3220-1YD12-0UF0	CONVERTER
G120XA (440V,IP20,1.5kW,C3,PN,Blanc,3C2)	6SL3220-1YD14-0CF0	CONVERTER
G120XA (440V,IP20,1.5kW,UF,PN,Blanc,3C2)	6SL3220-1YD14-0UF0	CONVERTER
G120XA (440V,IP20,2.2kW,C3,PN,Blanc,3C2)	6SL3220-1YD16-0CF0	CONVERTER
G120XA (440V,IP20,2.2kW,UF,PN,Blanc,3C2)	6SL3220-1YD16-0UF0	CONVERTER
G120XA (440V,IP20,3kW,C3,PN,Blanc,3C2)	6SL3220-1YD18-0CF0	CONVERTER
G120XA (440V,IP20,3kW,UF,PN,Blanc,3C2)	6SL3220-1YD18-0UF0	CONVERTER
G120XA (440V,IP20,4kW,C3,PN,Blanc,3C2)	6SL3220-1YD20-0CF0	CONVERTER
G120XA (440V,IP20,4kW,UF,PN,Blanc,3C2)	6SL3220-1YD20-0UF0	CONVERTER
G120XA (440V,IP20,5.5kW,C3,PN,Blanc,3C2)	6SL3220-1YD22-0CF0	CONVERTER
G120XA (440V,IP20,5.5kW,UF,PN,Blanc,3C2)	6SL3220-1YD22-0UF0	CONVERTER
G120XA (440V,IP20,7.5kW,C3,PN,Blanc,3C2)	6SL3220-1YD24-0CF0	CONVERTER
G120XA (440V,IP20,7.5kW,UF,PN,Blanc,3C2)	6SL3220-1YD24-0UF0	CONVERTER
G120XA (440V,IP20,11kW,C3,PN,Blanc,3C2)	6SL3220-1YD26-0CF0	CONVERTER
G120XA (440V,IP20,11kW,UF,PN,Blanc,3C2)	6SL3220-1YD26-0UF0	CONVERTER
G120XA (440V,IP20,15kW,C3,PN,Blanc,3C2)	6SL3220-1YD28-0CF0	CONVERTER
G120XA (440V,IP20,15kW,UF,PN,Blanc,3C2)	6SL3220-1YD28-0UF0	CONVERTER
G120XA (440V,IP20,18,5kW,C3,PN,Blanc,3C2)	6SL3220-1YD30-0CF0	CONVERTER
G120XA (440V,IP20,18,5kW,UF,PN,Blanc,3C2)	6SL3220-1YD30-0UF0	CONVERTER
G120XA (440V,IP20,22kW,C3,PN,Blanc,3C2)	6SL3220-1YD32-0CF0	CONVERTER
G120XA (440V,IP20,22kW,UF,PN,Blanc,3C2)	6SL3220-1YD32-0UF0	CONVERTER
G120XA (440V,IP20,30kW,C3,PN,Blanc,3C2)	6SL3220-1YD34-0CF0	CONVERTER
G120XA (440V,IP20,30kW,UF,PN,Blanc,3C2)	6SL3220-1YD34-0UF0	CONVERTER
G120XA (440V,IP20,37kW,C3,PN,Blanc,3C2)	6SL3220-1YD36-0CF0	CONVERTER
G120XA (440V,IP20,37kW,UF,PN,Blanc,3C2)	6SL3220-1YD36-0UF0	CONVERTER
G120XA (440V,IP20,45kW,C3,PN,Blanc,3C2)	6SL3220-1YD38-0CF0	CONVERTER
G120XA (440V,IP20,45kW,UF,PN,Blanc,3C2)	6SL3220-1YD38-0UF0	CONVERTER
G120XA (440V,IP20,55kW,C3,PN,Blanc,3C2)	6SL3220-1YD40-0CF0	CONVERTER
G120XA (440V,IP20,55kW,UF,PN,Blanc,3C2)	6SL3220-1YD40-0UF0	CONVERTER
G120XA (440V,IP20,75kW,C3,PN,Blanc,3C2)	6SL3220-1YD42-0CF0	CONVERTER
G120XA (440V,IP20,75kW,UF,PN,Blanc,3C2)	6SL3220-1YD42-0UF0	CONVERTER

G120XA (440V,IP20,90kW,C3,PN,Blanc,3C2)	6SL3220-1YD44-0CF0	CONVERTER
G120XA (440V,IP20,90kW,UF,PN,Blanc,3C2)	6SL3220-1YD44-0UF0	CONVERTER
G120XA (440V,IP20,110kW,C3,PN,Blanc,3C2)	6SL3220-1YD46-0CF0	CONVERTER
G120XA (440V,IP20,110kW,UF,PN,Blanc,3C2)	6SL3220-1YD46-0UF0	CONVERTER
G120XA (440V,IP20,132kW,C3,PN,Blanc,3C2)	6SL3220-1YD48-0CF0	CONVERTER
G120XA (440V,IP20,132kW,UF,PN,Blanc,3C2)	6SL3220-1YD48-0UF0	CONVERTER
G120XA (440V,IP20,160kW,C3,PN,Blanc,3C2)	6SL3220-1YD50-0CF0	CONVERTER
G120XA (440V,IP20,200kW,C3,PN,Blanc,3C2)	6SL3220-1YD52-0CF0	CONVERTER
G120XA (440V,IP20,250kW,C3,PN,Blanc,3C2)	6SL3220-1YD54-0CF0	CONVERTER
G120XA (440V,IP20,315kW,C3,PN,Blanc,3C2)	6SL3220-1YD56-0CF0	CONVERTER
G120XA (440V,IP20,355kW,C3,PN,Blanc,3C2)	6SL3220-1YD58-0CF0	CONVERTER
G120XA (440V,IP20,400kW,C3,PN,Blanc,3C2)	6SL3220-1YD60-0CF0	CONVERTER
G120XA (440V,IP20,0.75kW,C3,PN,BOP-2,3C2)	6SL3220-2YD10-0CF0	CONVERTER
G120XA (440V,IP20,0.75kW,UF,PN,BOP-2,3C2)	6SL3220-2YD10-0UF0	CONVERTER
G120XA (440V,IP20,1.1kW,C3,PN,BOP-2,3C2)	6SL3220-2YD12-0CF0	CONVERTER
G120XA (440V,IP20,1.1kW,UF,PN,BOP-2,3C2)	6SL3220-2YD12-0UF0	CONVERTER
G120XA (440V,IP20,1.5kW,C3,PN,BOP-2,3C2)	6SL3220-2YD14-0CF0	CONVERTER
G120XA (440V,IP20,1.5kW,UF,PN,BOP-2,3C2)	6SL3220-2YD14-0UF0	CONVERTER
G120XA (440V,IP20,2.2kW,C3,PN,BOP-2,3C2)	6SL3220-2YD16-0CF0	CONVERTER
G120XA (440V,IP20,2.2kW,UF,PN,BOP-2,3C2)	6SL3220-2YD16-0UF0	CONVERTER
G120XA (440V,IP20,3kW,C3,PN,BOP-2,3C2)	6SL3220-2YD18-0CF0	CONVERTER
G120XA (440V,IP20,3kW,UF,PN,BOP-2,3C2)	6SL3220-2YD18-0UF0	CONVERTER
G120XA (440V,IP20,4kW,C3,PN,BOP-2,3C2)	6SL3220-2YD20-0CF0	CONVERTER
G120XA (440V,IP20,4kW,UF,PN,BOP-2,3C2)	6SL3220-2YD20-0UF0	CONVERTER
G120XA (440V,IP20,5.5kW,C3,PN,BOP-2,3C2)	6SL3220-2YD22-0CF0	CONVERTER
G120XA (440V,IP20,5.5kW,UF,PN,BOP-2,3C2)	6SL3220-2YD22-0UF0	CONVERTER
G120XA (440V,IP20,7.5kW,C3,PN,BOP-2,3C2)	6SL3220-2YD24-0CF0	CONVERTER
G120XA (440V,IP20,7.5kW,UF,PN,BOP-2,3C2)	6SL3220-2YD24-0UF0	CONVERTER
G120XA (440V,IP20,11kW,C3,PN,BOP-2,3C2)	6SL3220-2YD26-0CF0	CONVERTER
G120XA (440V,IP20,11kW,UF,PN,BOP-2,3C2)	6SL3220-2YD26-0UF0	CONVERTER
G120XA (440V,IP20,15kW,C3,PN,BOP-2,3C2)	6SL3220-2YD28-0CF0	CONVERTER
G120XA (440V,IP20,15kW,UF,PN,BOP-2,3C2)	6SL3220-2YD28-0UF0	CONVERTER
G120XA (440V,IP20,18,5kW,C3,PN,BOP-2,3C2)	6SL3220-2YD30-0CF0	CONVERTER
G120XA (440V,IP20,18,5kW,UF,PN,BOP-2,3C2)	6SL3220-2YD30-0UF0	CONVERTER
G120XA (440V,IP20,22kW,C3,PN,BOP-2,3C2)	6SL3220-2YD32-0CF0	CONVERTER
G120XA (440V,IP20,22kW,UF,PN,BOP-2,3C2)	6SL3220-2YD32-0UF0	CONVERTER
G120XA (440V,IP20,30kW,C3,PN,BOP-2,3C2)	6SL3220-2YD34-0CF0	CONVERTER
G120XA (440V,IP20,30kW,UF,PN,BOP-2,3C2)	6SL3220-2YD34-0UF0	CONVERTER
G120XA (440V,IP20,37kW,C3,PN,BOP-2,3C2)	6SL3220-2YD36-0CF0	CONVERTER
G120XA (440V,IP20,37kW,UF,PN,BOP-2,3C2)	6SL3220-2YD36-0UF0	CONVERTER
G120XA (440V,IP20,45kW,C3,PN,BOP-2,3C2)	6SL3220-2YD38-0CF0	CONVERTER
G120XA (440V,IP20,45kW,UF,PN,BOP-2,3C2)	6SL3220-2YD38-0UF0	CONVERTER
G120XA (440V,IP20,55kW,C3,PN,BOP-2,3C2)	6SL3220-2YD40-0CF0	CONVERTER
G120XA (440V,IP20,55kW,UF,PN,BOP-2,3C2)	6SL3220-2YD40-0UF0	CONVERTER

G120XA (440V,IP20,75kW,C3,PN,BOP-2,3C2)	6SL3220-2YD42-0CF0	CONVERTER
G120XA (440V,IP20,75kW,UF,PN,BOP-2,3C2)	6SL3220-2YD42-0UF0	CONVERTER
G120XA (440V,IP20,90kW,C3,PN,BOP-2,3C2)	6SL3220-2YD44-0CF0	CONVERTER
G120XA (440V,IP20,90kW,UF,PN,BOP-2,3C2)	6SL3220-2YD44-0UF0	CONVERTER
G120XA (440V,IP20,110kW,C3,PN,BOP-2,3C2)	6SL3220-2YD46-0CF0	CONVERTER
G120XA (440V,IP20,110kW,UF,PN,BOP-2,3C2)	6SL3220-2YD46-0UF0	CONVERTER
G120XA (440V,IP20,132kW,C3,PN,BOP-2,3C2)	6SL3220-2YD48-0CF0	CONVERTER
G120XA (440V,IP20,132kW,UF,PN,BOP-2,3C2)	6SL3220-2YD48-0UF0	CONVERTER
G120XA (440V,IP20,160kW,C3,PN,BOP-2,3C2)	6SL3220-2YD50-0CF0	CONVERTER
G120XA (440V,IP20,200kW,C3,PN,BOP-2,3C2)	6SL3220-2YD52-0CF0	CONVERTER
G120XA (440V,IP20,250kW,C3,PN,BOP-2,3C2)	6SL3220-2YD54-0CF0	CONVERTER
G120XA (440V,IP20,315kW,C3,PN,BOP-2,3C2)	6SL3220-2YD56-0CF0	CONVERTER
G120XA (440V,IP20,355kW,C3,PN,BOP-2,3C2)	6SL3220-2YD58-0CF0	CONVERTER
G120XA (440V,IP20,400kW,C3,PN,BOP-2,3C2)	6SL3220-2YD60-0CF0	CONVERTER
G120XA (440V,IP20,0.75kW,C3,PN,IOP-2,3C2)	6SL3220-3YD10-0CF0	CONVERTER
G120XA (440V,IP20,0.75kW,UF,PN,IOP-2,3C2)	6SL3220-3YD10-0UF0	CONVERTER
G120XA (440V,IP20,1.1kW,C3,PN,IOP-2,3C2)	6SL3220-3YD12-0CF0	CONVERTER
G120XA (440V,IP20,1.1kW,UF,PN,IOP-2,3C2)	6SL3220-3YD12-0UF0	CONVERTER
G120XA (440V,IP20,1.5kW,C3,PN,IOP-2,3C2)	6SL3220-3YD14-0CF0	CONVERTER
G120XA (440V,IP20,1.5kW,UF,PN,IOP-2,3C2)	6SL3220-3YD14-0UF0	CONVERTER
G120XA (440V,IP20,2.2kW,C3,PN,IOP-2,3C2)	6SL3220-3YD16-0CF0	CONVERTER
G120XA (440V,IP20,2.2kW,UF,PN,IOP-2,3C2)	6SL3220-3YD16-0UF0	CONVERTER
G120XA (440V,IP20,3kW,C3,PN,IOP-2,3C2)	6SL3220-3YD18-0CF0	CONVERTER
G120XA (440V,IP20,3kW,UF,PN,IOP-2,3C2)	6SL3220-3YD18-0UF0	CONVERTER
G120XA (440V,IP20,4kW,C3,PN,IOP-2,3C2)	6SL3220-3YD20-0CF0	CONVERTER
G120XA (440V,IP20,4kW,UF,PN,IOP-2,3C2)	6SL3220-3YD20-0UF0	CONVERTER
G120XA (440V,IP20,5.5kW,C3,PN,IOP-2,3C2)	6SL3220-3YD22-0CF0	CONVERTER
G120XA (440V,IP20,5.5kW,UF,PN,IOP-2,3C2)	6SL3220-3YD22-0UF0	CONVERTER
G120XA (440V,IP20,7.5kW,C3,PN,IOP-2,3C2)	6SL3220-3YD24-0CF0	CONVERTER
G120XA (440V,IP20,7.5kW,UF,PN,IOP-2,3C2)	6SL3220-3YD24-0UF0	CONVERTER
G120XA (440V,IP20,11kW,C3,PN,IOP-2,3C2)	6SL3220-3YD26-0CF0	CONVERTER
G120XA (440V,IP20,11kW,UF,PN,IOP-2,3C2)	6SL3220-3YD26-0UF0	CONVERTER
G120XA (440V,IP20,15kW,C3,PN,IOP-2,3C2)	6SL3220-3YD28-0CF0	CONVERTER
G120XA (440V,IP20,15kW,UF,PN,IOP-2,3C2)	6SL3220-3YD28-0UF0	CONVERTER
G120XA (440V,IP20,18,5kW,C3,PN,IOP-2,3C2)	6SL3220-3YD30-0CF0	CONVERTER
G120XA (440V,IP20,18,5kW,UF,PN,IOP-2,3C2)	6SL3220-3YD30-0UF0	CONVERTER
G120XA (440V,IP20,22kW,C3,PN,IOP-2,3C2)	6SL3220-3YD32-0CF0	CONVERTER
G120XA (440V,IP20,22kW,UF,PN,IOP-2,3C2)	6SL3220-3YD32-0UF0	CONVERTER
G120XA (440V,IP20,30kW,C3,PN,IOP-2,3C2)	6SL3220-3YD34-0CF0	CONVERTER
G120XA (440V,IP20,30kW,UF,PN,IOP-2,3C2)	6SL3220-3YD34-0UF0	CONVERTER
G120XA (440V,IP20,37kW,C3,PN,IOP-2,3C2)	6SL3220-3YD36-0CF0	CONVERTER
G120XA (440V,IP20,37kW,UF,PN,IOP-2,3C2)	6SL3220-3YD36-0UF0	CONVERTER
G120XA (440V,IP20,45kW,C3,PN,IOP-2,3C2)	6SL3220-3YD38-0CF0	CONVERTER
G120XA (440V,IP20,45kW,UF,PN,IOP-2,3C2)	6SL3220-3YD38-0UF0	CONVERTER

G120XA (440V,IP20,55kW,C3,PN,IOP-2,3C2)	6SL3220-3YD40-0CF0	CONVERTER
G120XA (440V,IP20,55kW,UF,PN,IOP-2,3C2)	6SL3220-3YD40-0UF0	CONVERTER
G120XA (440V,IP20,75kW,C3,PN,IOP-2,3C2)	6SL3220-3YD42-0CF0	CONVERTER
G120XA (440V,IP20,75kW,UF,PN,IOP-2,3C2)	6SL3220-3YD42-0UF0	CONVERTER
G120XA (440V,IP20,90kW,C3,PN,IOP-2,3C2)	6SL3220-3YD44-0CF0	CONVERTER
G120XA (440V,IP20,90kW,UF,PN,IOP-2,3C2)	6SL3220-3YD44-0UF0	CONVERTER
G120XA (440V,IP20,110kW,C3,PN,IOP-2,3C2)	6SL3220-3YD46-0CF0	CONVERTER
G120XA (440V,IP20,110kW,UF,PN,IOP-2,3C2)	6SL3220-3YD46-0UF0	CONVERTER
G120XA (440V,IP20,132kW,C3,PN,IOP-2,3C2)	6SL3220-3YD48-0CF0	CONVERTER
G120XA (440V,IP20,132kW,UF,PN,IOP-2,3C2)	6SL3220-3YD48-0UF0	CONVERTER
G120XA (440V,IP20,160kW,C3,PN,IOP-2,3C2)	6SL3220-3YD50-0CF0	CONVERTER
G120XA (440V,IP20,200kW,C3,PN,IOP-2,3C2)	6SL3220-3YD52-0CF0	CONVERTER
G120XA (440V,IP20,250kW,C3,PN,IOP-2,3C2)	6SL3220-3YD54-0CF0	CONVERTER
G120XA (440V,IP20,315kW,C3,PN,IOP-2,3C2)	6SL3220-3YD56-0CF0	CONVERTER
G120XA (440V,IP20,355kW,C3,PN,IOP-2,3C2)	6SL3220-3YD58-0CF0	CONVERTER
G120XA (440V,IP20,400kW,C3,PN,IOP-2,3C2)	6SL3220-3YD60-0CF0	CONVERTER
G120XA (440V,IP00,450kW,C3,PN,Blanc,3C2)	6SL3225-1YD62-0CF0	CONVERTER
G120XA (440V,IP00,500kW,C3,PN,Blanc,3C2)	6SL3225-1YD64-0CF0	CONVERTER
G120XA (440V,IP00,560kW,C3,PN,Blanc,3C2)	6SL3225-1YD66-0CF0	CONVERTER
G120XA (440V,IP00,450kW,C3,PN,BOP-2,3C2)	6SL3225-2YD62-0CF0	CONVERTER
G120XA (440V,IP00,500kW,C3,PN,BOP-2,3C2)	6SL3225-2YD64-0CF0	CONVERTER
G120XA (440V,IP00,560kW,C3,PN,BOP-2,3C2)	6SL3225-2YD66-0CF0	CONVERTER
G120XA (440V,IP00,450kW,C3,PN,IOP-2,3C2)	6SL3225-3YD62-0CF0	CONVERTER
G120XA (440V,IP00,500kW,C3,PN,IOP-2,3C2)	6SL3225-3YD64-0CF0	CONVERTER
G120XA (440V,IP00,560kW,C3,PN,IOP-2,3C2)	6SL3225-3YD66-0CF0	CONVERTER

Compliance – applicable standards and other supporting documents

Evidence of compliance with applicable standards may be demonstrated by test reports, endorsed/accredited test reports, certification/competent body statements.

Having had regard to these documents, I am satisfied the above mentioned product complies with the requirements of the relevant ACMA Standards made under the *Radiocommunications Act 1992* and the *Telecommunications Act 1997*.

List the details of the documents the above statement was made, including the standard title and number

IEC 61800-3:2017 - Adjustable speed electrical power drive systems – Part 3: EMC requirements and specific test methods
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSA_1-5kW_C2_18-12-13.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSA_1-5kW_UF_18-12-13.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSA_3kW_C2_18-12-13.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSA_3kW_UF_18-12-13.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSB_7-5kW_C2_18-11-23.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSB_7-5kW_UF_18-11-23.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSC_15kW_C2_18-11-23.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSC_15kW_UF_18-11-23.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSD_22kW_C2_18-10-30.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSD_22kW_UF_18-10-31.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSD_37kW_C2_18-10-31.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSD_37kW_UF_18-10-31.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSE_55kW_C2_18-10-31.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSE_55kW_UF_18-10-31.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSF_90kW_C2_18-10-31.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSF_90kW_UF_18-10-31.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSF_132kW_C2_18-10-31.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSF_132kW_UF_18-10-31.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSG_250kW_C2_18-10-31.pdf
IEC_Report - G120X__400V__Type_Test_- _EMC_G120X_400V_IP20_FSG_250kW_C3_18-10-31.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP20_FSA_1_5kW_C3_18-12-13.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP20_FSA_1_5kW_UF_18-12-13.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP20_FSA_3kW_C3_18-12-13.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP20_FSA_3kW_UF_18-12-13.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP20_FSB_7_5kW_C3_18-11-30.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP20_FSC_15kW_UF_18-11-30.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP00_FSJ_560kW_C3_18-10-16.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP20_FSB_7_5kW_UF_18-11-30.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP20_FSC_15kW_C3_18-11-30.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP20_FSD_30kW_C3_18-10-01.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP20_FSD_30kW_UF_18-10-01.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP20_FSD_45kW_C3_18-10-04.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP20_FSD_45kW_UF_18-10-04.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP20_FSE_55kW_C3_18-10-04.pdf
IEC_Report - G120XA__440V__Type_Test_- _EMC_G120XA_440V_IP20_FSE_55kW_UF_18-10-05.pdf

IEC_Report - G120XA__440V__Type_Test - _EMC_G120XA_440V_IP20_FSF_90kW_C3_18-10-05.pdf
IEC_Report - G120XA__440V__Type_Test - _EMC_G120XA_440V_IP20_FSF_90kW_UF_18-10-05.pdf
IEC_Report - G120XA__440V__Type_Test - _EMC_G120XA_440V_IP20_FSF_132kW_C3_18-10-08.pdf
IEC_Report - G120XA__440V__Type_Test - _EMC_G120XA_440V_IP20_FSF_132kW_UF_18-10-09.pdf
IEC_Report - G120XA__440V__Type_Test - _EMC_G120XA_440V_IP20_FSG_250kW_C3_18-10-11.pdf
IEC_Report - G120XA__440V__Type_Test - _EMC_G120XA_440V_IP20_FSH_400kW_C3_18-10-19.pdf
Test_Report - EMC_G120X_FSH-J_400V_A5E44784421A_18-11-15.pdf
IEC_Report - EMC_G120X_400V_IP20_FSA_1-5kW_C2_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSA_1-5kW_UF_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSA_3kW_C2_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSA_3kW_UF_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSB_7-5kW_C2_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSB_7-5kW_UF_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSC_15kW_C2_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSC_15kW_UF_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSD_22kW_C2_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSD_22kW_UF_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSD_37kW_C2_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSD_37kW_UF_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSE_55kW_C2_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSE_55kW_UF_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSF_90kW_C2_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSF_90kW_UF_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSF_132kW_C2_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSF_132kW_UF_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSG_250kW_C2_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_400V_IP20_FSG_250kW_C3_V3.00_19-10-14.pdf
IEC_Report - EMC_G120X_690V_IP20_FSD_37kW_C2_V3.00_19-10-15.pdf
IEC_Report - EMC_G120X_690V_IP20_FSD_37kW_UF_V3.00_19-10-15.pdf
IEC_Report - EMC_G120X_690V_IP20_FSE_55kW_C2_V3.00_19-10-15.pdf
IEC_Report - EMC_G120X_690V_IP20_FSE_55kW_UF_V3.00_19-10-15.pdf
IEC_Report - EMC_G120X_690V_IP20_FSF_132kW_C3_V3.00_19-10-15.pdf
IEC_Report - EMC_G120X_690V_IP20_FSF_132kW_UF_V3.00_19-10-15.pdf
IEC_Report - EMC_G120X_690V_IP20_FSG_250kW_C3_V3.00_19-10-15.pdf
Test_Report - EMC_G120X_690V_FSH-J_IP20_A5E44784424A_18-11-15.pdf
IEC_Report - EMC_G120X_230V_IP20_FSA_1_5kW_UF.pdf.pdf
IEC_Report - EMC_G120X_230V_IP20_FSB_4kW_UF
IEC_Report - EMC_G120X_230V_IP20_FSC_7_5kW_UF.pdf
IEC_Report - EMC_G120X_230V_IP20_FSD_18_5kW_UF.pdf
IEC_Report - EMC_G120X_230V_IP20_FSE_30kW_UF.pdf
IEC_Report - EMC_G120X_230V_IP20_FSF_55kW_UF.pdf
Test_Report - EMC_G120X_400V_FSA-J_IP20_A5E44685849A_20-08-25.pdf
Test_Report - EMC_G120X_690V_FSD-J_IP20_A5E46445745A_20-08-25.pdf
IEC_Report - G120XA__440V__Type_Test - _EMC_G120XA_440V_IP00_FSJ_560kW_C3_PN_22-05-06.pdf
IEC_Report - G120XA__440V__Type_Test - _EMC_G120XA_440V_IP20_FSD_45kW_C3_PN_22-04-29.pdf
IEC_Report - G120XA__440V__Type_Test - _EMC_G120XA_440V_IP20_FSD_45kW_UF_PN_22-04-29.pdf
IEC_Report - G120XA__440V__Type_Test - _EMC_G120XA_440V_IP20_FSH_400kW_C3_PN_22-05-06.pdf

Declaration

I hereby declare that:

1. I am authorised to make this declaration on behalf of the Company mentioned above,
2. the contents of this form are true and correct, and
3. the product mentioned above complies with the applicable above mentioned standards and all products supplied under this declaration will be identical to the product identified above.

Note: Under section 137.1 of the *Criminal Code Act 1995*, it is an offence to knowingly provide false or misleading information to a Commonwealth entity.

Penalty: 12 months imprisonment

Date & SIGNATURE OF SUPPLIER OR AGENT	Product Manager POSITION IN ORGANISATION
---------------------------------------	--

The *Privacy Act 1988* (Cth) (the Privacy Act) imposes obligations on the ACMA in relation to the collection, security, quality, access, use and disclosure of personal information. These obligations are detailed in the Australian Privacy Principles.

The ACMA may only collect personal information if it is reasonably necessary for, or directly related to, one or more of the ACMA's functions or activities.

The purpose of collecting the personal information in this form is to ensure the supplier is identified in the 'Declaration of conformity'. If this Declaration of Conformity is not completed and the requested information is not provided, a compliance label cannot be applied.

Further information on the Privacy Act and the ACMA's Privacy Policy is available at www.acma.gov.au/privacypolicy. The Privacy Policy contains details about how you may access personal information about you that is held by the ACMA, and seek the correction of such information. It also explains how you may complain about a breach of the Privacy Act and how we will deal with such a complaint.

Should you have any questions in this regard, please contact the ACMA's privacy contact officer on telephone on 1800 226 667 or by email at privacy@acma.gov.au.