

The power of 4




Multiple alarming powered by 4 relays for over- or under-speed conditions from the sensors. Successfully **shut down** equipment and **protect** your processes.

Diverse functions, unified benefits

- **MFA** (motion failure alarm)
- **DSD** (Differential speed detection)
- **NCT** (Non-contacting tachometer)

SITRANS WM300 MFA

Reliable machine monitoring
One motion detection for **all** industries.



Enhanced simplicity

Intuitive programming thanks to a **simple menu** structure, along with an **on-board display** and **push buttons** for precise set point control of machines and processes. **No special training** required.

Super fast

Speed monitoring up to **7200 PPM**
with alarming from **0.15 to 3000 PPM**



un-matched detection range

Up to **4" (100mm)** sensor range to ferrous target with robust motion sensing probes.

