

Overview



Milltronics MSI is a heavy-duty, high accuracy full-frame single idler belt scale used for process and load-out control. Idler not included with belt scale.



Milltronics MMI is a heavy-duty, high accuracy multiple idler belt scale used for critical process and load-out control. Idler not included with belt scale.

Benefits

Milltronics MSI belt scale

- Outstanding accuracy and repeatability
- Unique parallelogram style load cell design
- Fast reaction to product loading; capable of monitoring fast moving belts
- Rugged construction
- SABS approval (South Africa), OIML, MID, and Measurement Canada

Milltronics MMI belt scale

- Exceptional accuracy and repeatability
- Unique parallelogram style load cell design
- Suitable for uneven or light product loading
- Capable of monitoring fast moving belts
- Low cost of ownership
- NTEP, OIML, MID, and Measurement Canada approved

Application

Milltronics MSI belt scale

Milltronics MSI belt scale provides continuous in-line weighing on a variety of products in primary and secondary industries. It is proven in a wide range of tough applications from extraction (in mines, quarries and pits), to power generation, iron and steel, food processing and chemicals. The MSI is suitable for monitoring such diverse products as sand, flour, coal, or sugar.

The MSI's proven use of parallelogram-style load cells results in fast reaction to vertical forces, ensuring instant response to product loading. This enables it to provide outstanding accuracy and repeatability even with uneven loading and fast belt speeds.

Operating with Milltronics BW500, SIWAREX WT241, WP241, or FTC microprocessor-based integrators, the MSI provides indication of flow rate, totalized weight, belt load, and belt speed of bulk solid materials. A speed sensor monitors conveyor belt speed for input to the integrator.

The MSI is installed in a simple drop-in operation and may be secured with just four bolts. An existing idler is then attached to the MSI dynamic beam. With no moving parts, maintenance is kept to a minimum, with just periodic calibration checks required.

Milltronics MMI belt scale

Milltronics MMI belt scale consists of two or more MSI single idler belt scales installed in series. It provides high accuracy continuous in-line weighing on a variety of products in primary and secondary industries. The MMI system is proven in a wide range of tough applications from extraction to power generation, iron and steel, food processing and chemicals. The MMI is suitable for monitoring such diverse products as fertilizer, sand, grain, flour, coal, or sugar.

The MMI's proven use of parallelogram-style load cells results in fast reaction to vertical forces, ensuring instant response to product loading. This enables it to provide outstanding accuracy and repeatability even with uneven or light loading, short idler spacing and fast belt speeds. Operating with Milltronics BW500 integrator (for custody transfer applications), the MMI provides indication of flow rate, total weight, belt load and belt speed of bulk solids materials on a belt conveyor. A speed sensor monitors conveyor belt speed for input to the integrator.

The MMI is installed in a simple drop-in operation and may be secured with just eight bolts and existing idler sets, secured to the dynamic beam. With no moving parts, maintenance is kept to a minimum, with just periodic calibration checks required.


Milltronics MSI and MMI

Design



Mounting

Note:

Conduit and cable arrangement may differ from example shown



MSI/MMI mounting



Mounting (two or more MSI units)

Selection and ordering data

Milltronics MSI Belt scale		Article No.									
Accuracy is ± 0.5 % or better of totalization over 20 ... 100 % operating range with capacity up to 12 000 t/h (13 200 STPH).		7MH7122-	●	●	●	●	●	-	●	●	●
Click on the Article No. for the online configuration in the PIA Life Cycle Portal.											
Scale construction											
Ordinary Locations/General Purpose (Non-Ex), CE, UKCA, RCM, EAC, KC		1									
CSA/FM Class II, Div. 1, Groups E, F, G, Class III; ATEX II 2 D Ex tb IIIC T90°C Db; UKEX II 2 D Ex tb IIIC T90°C Db; IECEX Ex tb IIIC T90°C Db; EAC Ex td A21 IP65 T90°C X; KCs Ex td A21 IP65 T90°C; CE, UKCA, RCM		2									
CSA/FM Class I, Div. 1, Groups A, B, C, D, Class II, Div. 1, Groups E, F, G, Class III; ATEX II 1 GD Ex ia IIC T4 Ga, ATEX II 1 GD Ex ia IIIC T135°C Da; UKEX II 1 GD Ex ia IIC T4 Ga, UKEX II 1 GD Ex ia IIIC T135°C Da; IECEX Ex ia IIC T4 Ga, IECEX Ex ia IIIC T135°C Da;		3									
ATEX I M1, ATEX II 1 GD Ex ia I Ma; UKEX I M1, UKEX II 1 GD Ex ia I Ma; IECEX Ex ia I Ma; MSHA		4									
Belt width and 'A' dimension											
<u>Belt widths from 18 ... 30 inch</u>											
18 inch, 'A' = 27 inch (686 mm)		A	A								
19 inch, 'A' = 28 inch (711 mm)		A	B								
20 inch, 'A' = 29 inch (737 mm)		A	C								
21 inch, 'A' = 30 inch (762 mm)		A	D								
22 inch, 'A' = 31 inch (787 mm)		A	E								
23 inch, 'A' = 32 inch (813 mm)		A	F								
24 inch, 'A' = 33 inch (838 mm)		A	G								
25 inch, 'A' = 34 inch (864 mm)		A	H								
26 inch, 'A' = 35 inch (889 mm)		A	J								
27 inch, 'A' = 36 inch (914 mm)		A	K								
28 inch, 'A' = 37 inch (940 mm)		A	L								
29 inch, 'A' = 38 inch (965 mm)		A	M								
30 inch, 'A' = 39 inch (991 mm)		A	N								
<u>Belt widths from 31 ... 50 inch</u>											
31 inch, 'A' = 40 inch (1 016 mm)		A	P								
32 inch, 'A' = 41 inch (1 041 mm)		A	Q								
33 inch, 'A' = 42 inch (1 067 mm)		A	R								
34 inch, 'A' = 43 inch (1 092 mm)		A	S								
35 inch, 'A' = 44 inch (1 118 mm)		A	T								
36 inch, 'A' = 45 inch (1 143 mm)		A	U								
37 inch, 'A' = 46 inch (1 168 mm)		A	V								
38 inch, 'A' = 47 inch (1 194 mm)		A	W								
39 inch, 'A' = 48 inch (1 219 mm)		B	A								
40 inch, 'A' = 49 inch (1 245 mm)		B	B								
41 inch, 'A' = 50 inch (1 270 mm)		B	C								
42 inch, 'A' = 51 inch (1 295 mm)		B	D								
43 inch, 'A' = 52 inch (1 321 mm)		B	E								
44 inch, 'A' = 53 inch (1 346 mm)		B	F								
45 inch, 'A' = 54 inch (1 372 mm)		B	G								
46 inch, 'A' = 55 inch (1 397 mm)		B	H								
47 inch, 'A' = 56 inch (1 422 mm)		B	J								
48 inch, 'A' = 57 inch (1 448 mm)		B	K								
49 inch, 'A' = 58 inch (1 473 mm)		B	L								
50 inch, 'A' = 59 inch (1 499 mm)		B	M								
<u>Belt widths from 51 ... 69 inch</u>											
51 inch, 'A' = 60 inch (1 524 mm)		B	N								
52 inch, 'A' = 61 inch (1 549 mm)		B	P								

Milltronics MSI and MMI

Selection and ordering data (continued)

Milltronics MSI Belt scale		Article No.									
Accuracy is $\pm 0.5\%$ or better of totalization over 20 ... 100 % operating range with capacity up to 12 000 t/h (13 200 STPH).		7MH7122- ● ● ● ● ● - ● ● ● ● ●									
53 inch, 'A' = 62 inch (1 575 mm)		B	Q								
54 inch, 'A' = 63 inch (1 600 mm)		B	R								
55 inch, 'A' = 64 inch (1 626 mm)		B	S								
56 inch, 'A' = 65 inch (1 651 mm)		B	T								
57 inch, 'A' = 66 inch (1 676 mm)		B	U								
58 inch, 'A' = 67 inch (1 702 mm)		B	V								
59 inch, 'A' = 68 inch (1 727 mm)		B	W								
60 inch, 'A' = 69 inch (1 753 mm)		C	A								
61 inch, 'A' = 70 inch (1 778 mm)		C	B								
62 inch, 'A' = 71 inch (1 803 mm)		C	C								
63 inch, 'A' = 72 inch (1 829 mm)		C	D								
64 inch, 'A' = 73 inch (1 854 mm)		C	E								
65 inch, 'A' = 74 inch (1 880 mm)		C	F								
66 inch, 'A' = 75 inch (1 905 mm)		C	G								
67 inch, 'A' = 76 inch (1 930 mm)		C	H								
68 inch, 'A' = 77 inch (1 956 mm)		C	J								
69 inch, 'A' = 78 inch (1 981 mm)		C	K								
<u>Belt widths from 70 ... 89 inch</u>											
70 inch, 'A' = 79 inch (2 007 mm)		C	L								
71 inch, 'A' = 80 inch (2 032 mm)		C	M								
72 inch, 'A' = 81 inch (2 057 mm)		C	N								
73 inch, 'A' = 82 inch (2 083 mm)		C	P								
74 inch, 'A' = 83 inch (2 108 mm)		C	Q								
75 inch, 'A' = 84 inch (2 134 mm)		C	R								
76 inch, 'A' = 85 inch (2 159 mm)		C	S								
77 inch, 'A' = 86 inch (2 184 mm)		C	T								
78 inch, 'A' = 87 inch (2 210 mm)		C	U								
79 inch, 'A' = 88 inch (2 235 mm)		C	V								
80 inch, 'A' = 89 inch (2 261 mm)		C	W								
81 inch, 'A' = 90 inch (2 286 mm)		D	A								
82 inch, 'A' = 91 inch (2 311 mm)		D	B								
83 inch, 'A' = 92 inch (2 337 mm)		D	C								
84 inch, 'A' = 93 inch (2 362 mm)		D	D								
85 inch, 'A' = 94 inch (2 388 mm)		D	E								
86 inch, 'A' = 95 inch (2 413 mm)		D	F								
87 inch, 'A' = 96 inch (2 438 mm)		D	G								
88 inch, 'A' = 97 inch (2 464 mm)		D	H								
89 inch, 'A' = 98 inch (2 489 mm)		D	J								
<u>Belt widths from 90 ... 96 inch</u>											
90 inch, 'A' = 99 inch (2 515 mm)		D	K								
91 inch, 'A' = 100 inch (2 540 mm)		D	L								
92 inch, 'A' = 101 inch (2 565 mm)		D	M								
93 inch, 'A' = 102 inch (2 591 mm)		D	N								
94 inch, 'A' = 103 inch (2 616 mm)		D	P								
95 inch, 'A' = 104 inch (2 642 mm)		D	Q								
96 inch, 'A' = 105 inch (2 667 mm)		D	R								
Load cell capacity											
Not specified ¹⁾						0					
25 lb (11.3 kg)						9			L	1	A
50 lb (22.7 kg)						1					
100 lb (45.4 kg)						2					
250 lb (113.4 kg)						3					
500 lb (226.8 kg)						4					
750 lb (340.2 kg)						5					
1 000 lb (453.6 kg)						6					

Selection and ordering data (continued)

Article No.									
7MH7122- ● ● ● ● ● - ● ● ● ● ●									
Milltronics MSI Belt scale Accuracy is ± 0.5 % or better of totalization over 20 ... 100 % operating range with capacity up to 12 000 t/h (13 200 STPH).									
1 250 lb (567 kg) ²⁾				7					
1 500 lb (680.4 kg) ²⁾				8					
2 000 lb (907.2 kg)				9				L	1 B
Fabrication									
C5-M rated polyester painted mild steel				1		1			
<u>Electro-galvanized mild steel:</u>									
18 ... 29 inch (457.2 ... 736.6 mm)				1		2			
30 ... 41 inch (762 ... 1 041.4 mm)				1		3			
42 ... 53 inch (1 066.8 ... 1 346.2 mm)				1		4			
54 ... 65 inch (1 371.6 ... 1 651 mm)				1		5			
66 ... 77 inch (1 676.4 ... 1 955.8 mm)				1		6			
78 ... 89 inch (1 981.2 ... 2 260.6 mm)				1		7			
90 ... 96 inch (2 286 ... 2 438.4 mm)				1		8			
<u>Stainless steel 304 (1.4301), bead blast finish (1 ... 6 µm, 40 ... 240 µin) for belt width scales:</u>									
18 ... 29 inch (457.2 ... 736.6 mm)				2		1			
30 ... 41 inch (762 ... 1 041.4 mm)				2		2			
42 ... 53 inch (1 066.8 ... 1 346.2 mm)				2		3			
54 ... 65 inch (1 371.6 ... 1 651 mm)				2		4			
66 ... 77 inch (1 676.4 ... 1 955.8 mm)				2		5			
78 ... 89 inch (1 981.2 ... 2 260.6 mm)				2		6			
90 ... 96 inch (2 286 ... 2 438.4 mm)				2		7			
<u>Stainless steel 316 (1.4401), bead blast finish (1 ... 6 µm, 40 ... 240 µin) for belt width scales:</u>									
18 ... 29 inch (457.2 ... 736.6 mm)				3		1			
30 ... 41 inch (762 ... 1 041.4 mm)				3		2			
42 ... 53 inch (1 066.8 ... 1 346.2 mm)				3		3			
54 ... 65 inch (1 371.6 ... 1 651 mm)				3		4			
66 ... 77 inch (1 676.4 ... 1 955.8 mm)				3		5			
78 ... 89 inch (1 981.2 ... 2 260.6 mm)				3		6			
90 ... 96 inch (2 286 ... 2 438.4 mm)				3		7			
C5-M rated polyester painted mild steel (compatible with MWL or flat bar weight calibration system)				4		1			
<u>Galvanized, for belt width scales:</u>									
(compatible with MWL or flat bar weight system)									
18 ... 29 inch (457.2 ... 736.6 mm)				4		2			
30 ... 41 inch (762 ... 1 041.4 mm)				4		3			
42 ... 53 inch (1 066.8 ... 1 346.2 mm)				4		4			
54 ... 65 inch (1 371.6 ... 1 651 mm)				4		5			
66 ... 77 inch (1 676.4 ... 1 955.8 mm)				4		6			
78 ... 89 inch (1 981.2 ... 2 260.6 mm)				4		7			
90 ... 96 inch (2 286 ... 2 438.4 mm)				4		8			
System specification									
Standard MSI and MMI							A		
NTEP Certified MMI ⁽³⁾⁽⁴⁾⁽⁵⁾							B		
OIML/MID Certified ⁽⁴⁾⁽⁵⁾							C		
MSI for MMI-3 ± 0.125 % accuracy ⁽⁶⁾							D		

Selection and ordering data	Order Code
Further designs	
Please add "-Z" to article no. and specify order code(s).	
Stainless steel tag [69 x 38 mm (2.7 x 1.5 inch)], Measuring-point number / identification (max 27 characters), specify in plain text.	Y15

Selection and ordering data	Order Code
Application Eng. reference number (max. 15 characters), specify in plain text.	Y31
Manufacturer's test certificate: According to EN 10204-2.2	C11
Factory test certificate	Y33

Milltronics MSI and MMI

Selection and ordering data (continued)

Selection and ordering data	Order Code
OIML/MID approval additional nameplate (submit application data with order) ⁵⁾	Y77
NTEP approval additional nameplate (submit application data with order) ⁵⁾	Y78
Extended cable length (For spare part pricing and part number consult factory)	A08
Load cell with 15 m (49.2 ft) cable length [standard is 3 m (9.8 ft)]	
High temp load cell (For spare part pricing and part number consult factory)	T50
Load cell suitable for high temp up to 175 °C (347 °F) [standard is 75 °C (167 °F)] ⁷⁾	
Load cell with 316 (1.4401) cover (For spare part pricing and part number consult factory)	H53
Load cell cover is constructed from 316 (1.4401) -stainless steel [standard is 304 (1.4301)]	
FDA compliant version	K01
Conduit and fittings designed for food applications -conforming to FDA/USDA standards	
Operating instructions	
All literature is available to download for free, in a range of languages, at http://www.siemens.com/weighing/documentation	
Spare parts	
Flat bar/MWL retrofit kit	Article No.
Conduit replacement kit	7MH7723-1FW
FDA conduit replacement kit	7MH7723-1NA
MWL calibration weight support brackets -galvanized	7MH7723-1QL
Ground cable	7MH7723-1JT
<u>Stainless steel load cells</u>	7MH3701-1AA1
<u>Standard load cell with 304 (1.4301) stainless steel cover</u>	
25 lb (11.3 kg)	A5E35801457
50 lb (22.7 kg)	PBD-23900246
100 lb (45.4 kg)	PBD-23900247
250 lb (113.4 kg)	PBD-23900248
500 lb (226.8 kg)	PBD-23900249
750 lb (340.2 kg)	PBD-23900250
1 000 lb (453.6 kg)	PBD-23900251
1 250 lb (567 kg)	A5E02235671
1 500 lb (680.4 kg)	A5E02239623
2 000 lb (907.2 kg)	A5E35801460
100 lb (45.4 kg), NTEP, OIML/MID	PBD-23900261
250 lb (113.4 kg), NTEP, OIML/MID	PBD-23900262
500 lb (226.8 kg), NTEP, OIML/MID	PBD-23900263
750 lb (340.2 kg), NTEP, OIML/MID	PBD-23900264
1 000 lb (453.6 kg), NTEP, OIML/MID	PBD-23900265
<u>Standard load cell with 304 (1.4301) stainless steel cover, includes mounting hardware</u>	
50 lb (22.7 kg)	7MH7725-1AC
100 lb (45.4 kg)	7MH7725-1AD
250 lb (113.4 kg)	7MH7725-1AE
500 lb (226.8 kg)	7MH7725-1AF
750 lb (340.2 kg)	7MH7725-1AG
1 000 lb (453.6 kg)	7MH7725-1AH
1 250 lb (567 kg)	7MH7725-1EA
1 500 lb (680.4 kg)	7MH7725-1EB
100 lb (45.4 kg), NTEP, OIML/MID	7MH7725-1DB

Selection and ordering data	Order Code
250 lb (113.4 kg), NTEP, OIML/MID	7MH7725-1DC
500 lb (226.8 kg), NTEP, OIML/MID	7MH7725-1DD
750 lb (340.2 kg), NTEP, OIML/MID	7MH7725-1DE
1 000 lb (453.6 kg), NTEP, OIML/MID	7MH7725-1DF
50 lb (22.7 kg), CSA/FM/ATEX/IECEX	7MH7725-1DT
100 lb (45.4 kg), CSA/FM/ATEX/IECEX	7MH7725-1DU
250 lb (113.4 kg), CSA/FM/ATEX/IECEX	7MH7725-1DV
500 lb (226.8 kg), CSA/FM/ATEX/IECEX	7MH7725-1DW
750 lb (340.2 kg), CSA/FM/ATEX/IECEX	7MH7725-1DX
1 000 lb (453.6 kg), CSA/FM/ATEX/IECEX	7MH7725-1DY
1 250 lb (567 kg), CSA/FM/ATEX/IECEX	7MH7725-1EE
1 500 lb (680.4 kg), CSA/FM/ATEX/IECEX	7MH7725-1EF
<u>Load cell with 316 (1.4401) stainless steel cover</u>	
25 lb (11.3 kg)	PBD-25851-A8H53
50 lb (22.7 kg)	PBD-25851-A0H53
100 lb (45.4 kg)	PBD-25851-A1H53
250 lb (113.4 kg)	PBD-25851-A2H53
500 lb (226.8 kg)	PBD-25851-A3H53
750 lb (340.2 kg)	PBD-25851-A4H53
1 000 lb (453.6 kg)	PBD-25851-A5H53
1 250 lb (567 kg)	PBD-25851-A6H53
1 500 lb (680.4 kg)	PBD-25851-A7H53
2 000 lb (907.2 kg)	PBD-25851-A9H53
100 lb (45.4 kg), NTEP, OIML/MID	PBD-25851-B1H53
250 lb (113.4 kg), NTEP, OIML/MID	PBD-25851-B2H53
500 lb (226.8 kg), NTEP, OIML/MID	PBD-25851-B3H53
750 lb (340.2 kg), NTEP, OIML/MID	PBD-25851-B4H53
1 000 lb (453.6 kg), NTEP, OIML/MID	PBD-25851-B5H53
<u>Load cell, high temperature up to 175 °C (347 °F)</u>	
25 lb (11.3 kg)	PBD-25851-A8T50
50 lb (22.7 kg)	PBD-25851-A0T50
100 lb (45.4 kg)	PBD-25851-A1T50
250 lb (113.4 kg)	PBD-25851-A2T50
500 lb (226.8 kg)	PBD-25851-A3T50
750 lb (340.2 kg)	PBD-25851-A4T50
1 000 lb (453.6 kg)	PBD-25851-A5T50
1 250 lb (567 kg)	PBD-25851-A6T50
1 500 lb (680.4 kg)	PBD-25851-A7T50
2 000 lb (907.2 kg)	PBD-25851-A9T50
<u>Load cell, high temperature up to 175 °C (347 °F) with 316 (1.4401) stainless steel cover</u>	
25 lb (11.3 kg)	PBD-25851-A8TH
50 lb (22.7 kg)	PBD-25851-A0TH
100 lb (45.4 kg)	PBD-25851-A1TH
250 lb (113.4 kg)	PBD-25851-A2TH
500 lb (226.8 kg)	PBD-25851-A3TH
750 lb (340.2 kg)	PBD-25851-A4TH
1 000 lb (453.6 kg)	PBD-25851-A5TH
1 250 lb (567 kg)	PBD-25851-A6TH
1 500 lb (680.4 kg)	PBD-25851-A7TH
2 000 lb (907.2 kg)	PBD-25851-A9TH
<u>Load cell with 15 m (49.2 ft) cable length</u>	

Selection and ordering data (continued)

Selection and ordering data	Order Code
25 lb (11.3 kg)	PBD-25851-A8A08
50 lb (22.7 kg)	PBD-25851-A0A08
100 lb (45.4 kg)	PBD-25851-A1A08
250 lb (113.4 kg)	PBD-25851-A2A08
500 lb (226.8 kg)	PBD-25851-A3A08
750 lb (340.2 kg)	PBD-25851-A4A08
1 000 lb (453.6 kg)	PBD-25851-A5A08
1 250 lb (567 kg)	PBD-25851-A6A08
1 500 lb (680.4 kg)	PBD-25851-A7A08
2 000 lb (907.2 kg)	PBD-25851-A9A08
100 lb (45.4 kg), NTEP, OIML/MID	PBD-25851-B1A08
250 lb (113.4 kg), NTEP, OIML/MID	PBD-25851-B2A08
500 lb (226.8 kg), NTEP, OIML/MID	PBD-25851-B3A08
750 lb (340.2 kg), NTEP, OIML/MID	PBD-25851-B4A08
1 000 lb (45.4 kg), NTEP, OIML/MID	PBD-25851-B5A08
<u>Load cell with 15 m (49.2 ft) cable length and 316 (1.4401) stainless steel cover</u>	
25 lb (11.3 kg)	PBD-25851-A8AH
50 lb (22.7 kg)	PBD-25851-A0AH
100 lb (45.4 kg)	PBD-25851-A1AH
250 lb (113.4 kg)	PBD-25851-A2AH
500 lb (226.8 kg)	PBD-25851-A3AH
750 lb (340.2 kg)	PBD-25851-A4AH
1 000 lb (453.6 kg)	PBD-25851-A5AH
1 250 lb (567 kg)	PBD-25851-A6AH
1 500 lb (680.4 kg)	PBD-25851-A7AH
2 000 lb (907.2 kg)	PBD-25851-A9AH
100 lb (45.4 kg), NTEP, OIML/MID	PBD-25851-B1AH
250 lb (113.4 kg), NTEP, OIML/MID	PBD-25851-B2AH
500 lb (226.8 kg), NTEP, OIML/MID	PBD-25851-B3AH
750 lb (340.2 kg), NTEP, OIML/MID	PBD-25851-B4AH
1 000 lb (453.6 kg), NTEP, OIML/MID	PBD-25851-B5AH
<u>Load cell, high temperature up to 175 °C (347 °F) with 15 m (49.2 ft) cable length</u>	
25 lb (11.3 kg)	PBD-25851-A8TA
50 lb (22.7 kg)	PBD-25851-A0TA
100 lb (45.4 kg)	PBD-25851-A1TA
250 lb (113.4 kg)	PBD-25851-A2TA
500 lb (226.8 kg)	PBD-25851-A3TA
750 lb (340.2 kg)	PBD-25851-A4TA
1 000 lb (453.6 kg)	PBD-25851-A5TA
1 250 lb (567 kg)	PBD-25851-A6TA
1 500 lb (680.4 kg)	PBD-25851-A7TA
2 000 lb (907.2 kg)	PBD-25851-A9TA

Selection and ordering data	Order Code
<u>Load cell, high temperature up to 175 °C (347 °F) with 15 m (49.2 ft) cable length and 316 (1.4401) stainless steel cover</u>	
25 lb (11.3 kg)	PBD-25851-A8AHT
50 lb (22.7 kg)	PBD-25851-A0AHT
100 lb (45.4 kg)	PBD-25851-A1AHT
250 lb (113.4 kg)	PBD-25851-A2AHT
500 lb (226.8 kg)	PBD-25851-A3AHT
750 lb (340.2 kg)	PBD-25851-A4AHT
1 000 lb (453.6 kg)	PBD-25851-A5AHT
1 250 lb (567 kg)	PBD-25851-A6AHT
1 500 lb (680.4 kg)	PBD-25851-A7AHT
2 000 lb (907.2 kg)	PBD-25851-A9AHT
Idler clips	
5 inch (127 mm) for 27 ... 62 inch (686 ... 1 575 mm) "A" dimensions	7MH7723-1BT
7 inch (178 mm) for 63 ... 74 inch (1 600 ... 1 880 mm) "A" dimensions	7MH7723-1DF
Calibration weights	
6.0 lb/ 2.7 kg	7MH7724-1AB
18 lb/ 8.2 kg	7MH7724-1AA
See Milltronics flat bar calibration weights catalog sheet: https://support.industry.siemens.com/cs/document/109813400	
Note: calibration accessories should be ordered as a separate line order.	
Intrinsically safe barriers for use with IS mining approvals	
Mild steel enclosure, with 24 V DC speed sensor barrier	A5E50771080
Stainless steel enclosure, with 24 V DC speed sensor barrier	A5E50771081

- 1) Only for quotation purposes, not a valid ordering option.
- 2) Available with Fabrication options 11 ... 18 and 41 ... 48 only, and with System specification option A only.
- 3) Two MSI are required to make the NTEP approved MMI.
- 4) Approval available with load cell options 2 ... 6 only and applicable BW500.
- 5) Complete specification data sheet on page 4/27 and submit with order "legal for trade" version.
- 6) Includes metrological approved load cells.
- 7) Not available with construction option 2, or system specification options B, C, D.
- 8) Barrier contains connections for MMI-2 and speed sensor.

Milltronics MSI and MMI

Technical specifications

Milltronics MSI and MMI	
Mode of operation	
Measuring principle	Strain gauge load cells measuring load on belt conveyor idler(s)
Typical application	
• MSI	Control in fractionated stone blending tunnels
• MMI	Custody transfer
Measurement accuracy	
Accuracy ¹⁾	
• MSI	± 0.5 % or better of totalization over 20 ... 100 % operating range
• MMI-2 (2 idler)	± 0.25 % or better of totalization over 20 ... 100 % operating range
• MMI-3 (3 idler)	± 0.125 % or better of totalization over 25 ... 100 % operating range
<i>Note: available with system specification option D only</i>	
Repeatability	± 0.1 %
Medium conditions	
Material temperature	-50 ... +200 °C (-58 ... +392 °F)
Belt design	
Belt width	• 18 ... 96 inch in CEMA sizes²⁾ • Equivalent to 500 ... 2 400 mm in metric size²⁾ • Refer to dimensions section
Belt speed	Up to 5 m/s (1 000 fpm) ²⁾
Capacity	Up to 12 000 t/h (13 200 STPH) at maximum belt speed. Please contact a Siemens representative for higher rates. ²⁾
Conveyor incline	• ± 20° from horizontal, fixed incline • Up to ± 30° with reduced accuracy³⁾
Idlers	
Idler profile	• Flat to 35° • Up to 45° with reduced accuracy³⁾
Idler diameter	50 ... 180 mm (2 ... 7 inch)
Idler spacing	0.5 ... 1.5 m (1.5 ... 5.0 ft)
Load cell	
Construction	Stainless steel construction with 304 (1.4301) stainless steel cover Strain gauge protection: polybutadiene
Degree of protection	IP67, IP65 on hazardous approved models
Cable length	3 m (10 ft) Note: to calculate installation cable length subtract 3 048 mm (120 inch) from the "A" dimension
Excitation	10 V DC nominal, 15 V DC maximum
Output	2 ± 0.002 mV/V excitation (nominal) at rated load cell capacity
Non-linearity and hysteresis	0.02 % of rated output
Non-repeatability	0.01 % of rated output
Capacity	
• Maximum ranges	25, 50, 100, 250, 500, 750, 1 000, 1 250, 1 500, 2 000 lb
Overload	150 % of rated capacity, ultimate 300 % of rated capacity
Temperature	• -50 ... +75 °C (-58 ... +167 °F) operating range, optional -50 ... +175 °C (-58 ... 347 °F) • -40 ... +65 °C (-40 ... +150 °F) compensated • -10 ... +40 °C (14 ... 104 °F) compensated on trade approved versions
Weight	See dimensions section

Technical specifications (continued)

Milltronics MSI and MMI	
Interconnection wiring (to integrator, per MSI)	< 150 m (500 ft) 18 AWG (0.75 mm ²) 6 conductor shielded cable > 150 ... 300 m (500 ... 1 000 ft) 18 ... 22 AWG (0.75 ... 0.34 mm ²), 8 conductor shielded cable
Approvals	• CSA/IM Class II, Div. 1, Groups A, B, C, D, Class II, Div. 1, Groups E, F, G, Class III; • ATEX I M1 Ex ia I Ma, ATEX II 1 GD Ex ia IIC T4 Ga, ATEX II 1 GD Ex ia IIIC T135°C Da, ATEX II 2 D Ex tb IIIC T90°C Db; • UKEX I M1 Ex ia I Ma, UKEX II 1 GD Ex ia IIC T4 Ga, UKEX II 1 GD Ex ia IIIC T135°C Da, UKEX II 2 D Ex tb IIIC T90°C Db; • IECEx Ex ia I Ma, IECEx Ex ia IIC T4 Ga, IECEx Ex ia IIIC T135°C Da, IECEx Ex tb IIIC T90°C Db; • EAC Ex Ex tD A21 IP65 T90°C X; • KCs Ex tD A21 IP65 T90°C; • MSHA; • CE, UKCA, RCM, EAC, KC, CMC, RTN
Metrology approvals	Measurement Canada, MID, OIML, SABS ⁴⁾ , NTEP ⁵⁾ , STAMEQ, GOST

¹⁾ Accuracy subject to: on factory approved installations the belt scale system's totalized weight will be within the specified accuracy when compared to a known weighed material test sample. The test rate must be within the specified range of the design capacity and held constant for the duration of the test. The minimum material test sample must be equivalent to a sample obtained at the test flow rate for three revolutions of the belt or at least ten minutes running time, whichever is greater.


²⁾ Contact Siemens (http://www.automation.siemens.com/aspa_app) for consideration of higher values.

³⁾ Review by Siemens required (http://www.automation.siemens.com/aspa_app).

⁴⁾ MSI only.

⁵⁾ MMI only.

Dimensional drawings



MSI dimensions


Conveyor belt width	Mounting scale width A	Minimum drop-in width B	C	D	E	Weight (approx.)
18 inch (457 mm)	27 inch (686 mm)	23.25 inch (591 mm)	9.5 inch (241 mm)	5.5 inch (140 mm)	7 inch (178 mm)	82 lb (37 kg)
20 inch (508 mm)	29 inch (737 mm)	25.25 inch (641 mm)	9.5 inch (241 mm)	5.5 inch (140 mm)	7 inch (178 mm)	85 lb (39 kg)
24 inch (610 mm)	33 inch (838 mm)	29.25 inch (743 mm)	9.5 inch (241 mm)	5.5 inch (140 mm)	7 inch (178 mm)	90 lb (41 kg)
30 inch (762 mm)	39 inch (991 mm)	35.25 inch (895 mm)	9.5 inch (241 mm)	5.5 inch (140 mm)	7 inch (178 mm)	99 lb (45 kg)
36 inch (914 mm)	45 inch (1 143 mm)	41.25 inch (1 048 mm)	9.5 inch (241 mm)	5.5 inch (140 mm)	7 inch (178 mm)	107 lb (49 kg)
42 inch (1 067 mm)	51 inch (1 295 mm)	47.25 inch (1 200 mm)	9.5 inch (241 mm)	5.5 inch (140 mm)	7 inch (178 mm)	116 lb (53 kg)
48 inch (1 219 mm)	57 inch (1 448 mm)	53.25 inch (1 353 mm)	9.5 inch (241 mm)	5.5 inch (140 mm)	7 inch (178 mm)	125 lb (57 kg)
54 inch (1 372 mm)	63 inch (1 600 mm)	59.25 inch (1 505 mm)	12 inch (305 mm)	8 inch (203 mm)	7 inch (178 mm)	175 lb (79 kg)
60 inch (1 524 mm)	69 inch (1 753 mm)	65.25 inch (1 657 mm)	12 inch (305 mm)	8 inch (203 mm)	7 inch (178 mm)	193 lb (88 kg)
66 inch (1 676 mm)	75 inch (1 905 mm)	71.25 inch (1 810 mm)	12 inch (305 mm)	8 inch (203 mm)	8 inch (203 mm)	229 lb (104 kg)
72 inch (1 829 mm)	81 inch (2 057 mm)	77.25 inch (1 962 mm)	12 inch (305 mm)	8 inch (203 mm)	8 inch (203 mm)	247 lb (112 kg)

Other widths available - check configuration information. Sizes are from 18 inch (457 mm) to 96 inch (2 438 mm) in 1 inch (25.4 mm) increments. All sizes are nominal.

Note: dimension B must be approx. 3/8 inch or 10 mm less than Y dimension of the conveyor (see Application Questionnaire at <http://www.siemens.com/weighing/application-questionnaires>).

Milltronics MSI and MMI

Circuit diagrams



MSI/MMI connections

More information

NTEP/Measurement Canada/OIML & MID Specification Data

Please complete and submit the relevant details listed below when ordering NTEP, Measurement Canada, or OIML & MID approval options	Value
NTEP	
Maximum rated capacity (TPH)	
Minimum rated capacity (TPH)	
Belt speed (FPM)	
Scale division (tons)	
Maximum loading (lb/ft)	
Measurement Canada	
Rate	
Speed (min/max m/s, FPM)	
Test load (kg/m, lb/ft)	
OIML & MID	
Totalization scale interval (tonnes)	
Belt speed max/min (m/s)	
Maximum flow rate (MTPH)	
Minimum flow rate (MTPH)	
Minimum totalized load (tonnes)	
Product to be weighed	
Maximum capacity (tonnes)	
Weigh length (m)	
Ratio between minimum net load and maximum capacity	
Zero testing should have a duration of at least () revolutions	